

Radial grippers HGRT, heavy-duty

FESTO



Radial grippers HGRT, heavy-duty

Key features


FESTO

At a glance

- Sturdy and precise kinematics for maximum torque resistance and long service life
- The virtually backlash-free plain-bearing guide is realised using ground-in gripper jaws
- Systematic use of high-performance and lightweight materials
- The force generated by the linear motion is translated into the gripper jaw movement via a slotted guide system at the piston rod. This also guarantees synchronous movement of the gripper jaws
- The opening angle of the gripper jaws is freely adjustable up to max. 90° per gripper finger. This reduces the cycle time and prevents possible collisions due to the gripper jaws opening too wide
- Can be used as a double-acting or single-acting gripper
- Compression spring for supplementary or retaining gripping forces
- Suitable for external and internal gripping
- Wide range of options for mounting on drives

Flexible stroke limitation

As radial gripper



The gripper as delivered features a fixed stop that enables an opening angle of 180°.


As angle gripper with adjustable stroke



The stroke reducing kit HGRT-HR, which can be ordered as an accessory, enables the opening angle to be reduced by means of an adjustment screw. This provides an easy means of converting the radial gripper into an angle gripper.


Additional ports

For sealing air



Compressed air flows past the gripper jaw when sealing air (max. 0.5 bar) is connected. This prevents particles, for example, from entering the gripper jaw guide.

For lubrication



The ports can also be used to re-lubricate the guide.

Position sensing/force control

With position transmitter SMAT-8M



Infinite position sensing possible

- Analogue output 0 ... 10 V

With proportional pressure regulator VPPM



Infinite adjustment of the gripping force possible

- Setpoint input
 - 0 ... 10 V
 - 4 ... 20 mA

With proximity sensor SMT-8G/-10G



Multiple positions can be sensed:


- Open
- Closed
- Workpiece gripped

Radial grippers HGRT, heavy-duty


Key features

FESTO

Supply ports
Direct




Via adapter plate




- - Note
Gripper selection
sizing software
→ www.festo.com

Mounting options



Direct mounting
From the side




On front face



- - Note
Radial grippers are not designed for
the following sample applications:



• Welding splashes




Radial grippers HGRT, heavy-duty


Peripherals overview

FESTO


Peripherals overview



System product for handling and assembly technology



Proportional pressure regulator VPPM



Accessories		
Type	Brief description	➔ Page/Internet
[1] Stroke reducing kit HGRT-HR	For adjusting the opening angle	20
[2] Centring sleeve ZBH	<ul style="list-style-type: none"> For centring when attaching gripper fingers 4 included in the scope of delivery of the gripper 	21
[3] Proximity sensor SIEN	For sensing the piston position	22
[4] Sensor bracket DASI	<ul style="list-style-type: none"> For mounting the proximity sensors SIEN on the gripper The scope of delivery of the sensor bracket includes switch lugs 	20
[5] Proximity sensor SMT-8G/-10G	<ul style="list-style-type: none"> For sensing the piston position The proximity sensor is flush with the housing at the bottom 	21
[6] Position transmitter SMAT-8M	<ul style="list-style-type: none"> Continuously senses the position of the piston. It has an analogue output with an output signal that is proportional to the piston position. For size 40 	21
[7] One-way flow control valve GRLA	For regulating speed	grla
[8] Push-in fitting QS	For connecting compressed air tubing with standard O.D.	quick star
[9] Centring sleeve ZBH	For centring when attaching to a drive or plate	21
[10] Adapter kit DHAA	Connecting plate between drive and gripper	17
[11] Proportional pressure regulator VPPM	For infinite adjustment of the gripping force	vppm

Radial grippers HGRT, heavy-duty

Type codes




		HGRT	—	16	—	A	—	
Type								
HGRT	Radial gripper							
Size								
Position sensing								
A	Via proximity sensor							
Gripping force retention								
G2	Closing							


Radial grippers HGRT, heavy-duty

Technical data

FESTO

Function
Double-acting
HGRT...



- Ø -  12 ... 50 mm

- | - 

180°

Function – Variants
Single-acting or with gripping force retention



Wearing parts kits
→ 16



General technical data										
Size			16	20	25	32	40	50		
Design			Force-guided motion sequence							
Mode of operation			Double-acting							
Gripper function			Radial							
Number of gripper jaws			2							
Max. opening angle			[°] 180							
Pneumatic connection			M3	M5	M5	M5	G1/8	G1/8		
Repetition accuracy ¹⁾			[mm] ≤ 0.02							
Max. interchangeability			[mm] ≤ 0.2							
Max. gripper jaw backlash ²⁾			[mm] ≤ 0.1							
Max. gripper jaw angular backlash ³⁾			[°] ≤ 0.1							
Max. permitted working frequency			[Hz] ≤ 3					≤ 2		
Rotational symmetry			[mm] ≤ Ø 0.2							
Position sensing			Via proximity sensor, position transmitter							
			Via inductive proximity sensor							
Type of mounting			Via female thread and centring sleeve							
Mounting position			Any							
Product weight			–	[g]	130	290	540	840	1,580	3,100
			G2	[g]	150	320	610	940	1,770	3,500

- 1) End-position drift under constant conditions of use with 100 consecutive strokes in the direction of movement of the gripper jaws
 2) Perpendicular to the direction of motion of the gripper jaws
 3) Preloaded, backlash-free ball bearing guide

Operating and environmental conditions			
Operating pressure	– [bar]	3 ... 8	
	G2 [bar]	4 ... 8	
Operating medium		Compressed air in accordance with ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium		Operation with lubricated medium possible (in which case lubricated operation will always be required)	
Ambient temperature ¹⁾	[°C]	+5 ... +60	
Corrosion resistance class CRC ²⁾		2	

- 1) Note operating range of proximity sensors
 2) Corrosion resistance class 2 according to Festo standard 940 070
 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.


Radial grippers HGRT, heavy-duty

Technical data

FESTO

Materials


Sectional view



Radial gripper

1	Gripper jaw	Hardened steel
2	Housing	Smooth anodised aluminium
3	Piston	Anodised aluminium
–	Seals	Polyurethane, nitrile rubber
–	Note on materials	Free of copper, PTFE and silicone
		RoHS-compliant


Total gripping torque at 6 bar



The gripping torque is not constant within the opening angle → 12.

Size		16	20	25	32	40	50
Opening	[Ncm]	188	588	1,348	2,024	3,892	8,424
Closing	[Ncm]	158	516	1,208	1,856	3,526	7,754

Static characteristic load values at the gripper jaws



The indicated permissible forces and torques apply to a single gripper jaw. The indicated values include the lever arm, additional applied loads caused by the workpiece or external gripper

fingers, as well as forces which occur during movement.

The zero co-ordinate line (gripper jaw guide) must be taken into consideration for the calculation of torques.


Size		16	20	25	32	40	50
Max. permissible force F_z	[N]	50	100	180	280	400	1,200
Max. permissible torque M_y	[Nm]	3.9	6.2	10	13.5	17.5	35
Max. permissible torque M_z	[Nm]	0.3	0.5	1	1.3	1.6	10

Radial grippers HGRT, heavy-duty

Technical data

FESTO


Mass moment of inertia [kgm²x10⁻⁴]



Mass moment of inertia of the radial gripper referred to the central axis, without external gripper fingers, without load.

Size		16	20	25	32	40	50
HGRT	–	0.191	0.74	2.1	4.62	13.87	43.39
	G2	0.21	0.81	2.33	5.03	15.26	47.70

Opening and closing times [ms] at 6 bar



The indicated opening and closing times [ms] have been measured at room temperature and 6 bar operating pressure with vertically mounted gripper and without external gripper fingers.

The grippers must be throttled for greater applied loads. Opening and closing times must then be adjusted accordingly.

Size			16	20	25	32	40	50
Without external gripper fingers								
HGRT	–	Opening	246	280	309	359	283	350
	–	Closing	293	308	343	403	320	403
HGRT	G2	Opening	233	372	443	503	370	490
	G2	Closing	185	295	301	337	270	355


Radial grippers HGRT, heavy-duty

Technical data


FESTO

Permissible mass moment of inertia J with external gripper fingers as a function of opening and closing times t at 6 bar


HGRT-16-A




HGRT-20-A




HGRT-25-A




HGRT-32-A



HGRT-40-A



HGRT-50-A



Radial grippers HGRT, heavy-duty


Technical data

FESTO

Gripping force F_H per gripper jaw as a function of operating pressure and lever arm x


Gripping forces as a function of the operating pressure and the lever arm can be determined for the size using the following graph.

The gripping torque is not constant within the opening angle $\rightarrow 12^\circ$.




External gripping (closing)


HGRT-16-A




HGRT-20-A




HGRT-25-A




HGRT-32-A



HGRT-40-A



HGRT-50-A



— 3 bar
- - - 6 bar
- · - 8 bar

Radial grippers HGRT, heavy-duty


Technical data

FESTO

Gripping force F_H per gripper jaw as a function of operating pressure and lever arm x


Gripping forces as a function of the operating pressure and the lever arm can be determined for the size using the following graph.

The gripping torque is not constant within the opening angle $\rightarrow 12$.




Internal gripping (opening)


HGRT-16-A




HGRT-20-A




HGRT-25-A




HGRT-32-A



HGRT-40-A



HGRT-50-A



- 3 bar
- - - 6 bar
- · - 8 bar

Radial grippers HGRT, heavy-duty

Technical data


FESTO

Gripping force F_H per gripper jaw at 6 bar as a function of lever arm x and eccentricity a and b

The following formula must be used to calculate the lever arm x with eccentric gripping:

$$x = \sqrt{a^2 + b^2}$$

The gripping force F_H can be read from the graphs (→ from page 10) using the calculated value x .



Calculation example

Given:

Distance $a = 45$ mm

Distance $b = 40$ mm

To be calculated:

The gripping force at 6 bar,
with an HGRT-40,
used as an external gripper


Procedure:

Calculating the lever arm x

$$x = \sqrt{45^2 + 40^2}$$


$x = 60$ mm

The graph (→ 10) gives a value of F_H
= 300 N for the gripping force.



Torque curve M as a function of opening angle α

The drive principle of the gripper jaws means that the torque is not constant within the opening angle. The percentage of torque available in each case can be seen in the graph. An opening angle of 0° means a parallel gripper jaw position.




Radial grippers HGRT, heavy-duty

Technical data

FESTO


Spring torque M_F as a function of opening angle α

HGRT-16 ... 25



— HGRT-16-A-G2
- - - HGRT-20-A-G2
- · - HGRT-25-A-G2

HGRT-32 ... 40



— HGRT-32-A-G2
- - - HGRT-40-A-G2
- · - HGRT-50-A-G2

Determining the actual gripping torques $M_{Grtotal}$ for HGRT-...-G2 as a function of the application

The radial gripper with integrated spring, HGRT-...-G2 (closing gripping force retention), can be used as a:

- Single-acting gripper
- Gripper with supplementary gripping force
- Gripper with gripping force retention

To calculate the available gripping torque $M_{Grtotal}$ (per gripper jaw), the data from the graphs for the gripping force F_H (→ 10/11), the torque curve

M (→ 12) and the spring torque M_F (→ 13) must be combined accordingly.

$$M_{Gr} = F_H \cdot x \cdot M \text{ [%]}$$

M_{Gr} Gripping torque
 F_H Gripping force
 x Lever arm
 M Torque curve

Application

Single-acting

- Gripping with spring force:
 $M_{Grtotal} = M_F$
- Gripping with pressure force:
 $M_{Grtotal} = M_{Gr} - M_F$

Supplementary gripping force

- Gripping with pressure and spring force:
 $M_{Grtotal} = M_{Gr} + M_F$

Gripping force retention

- Gripping with spring force:
 $M_{Grtotal} = M_F$


Radial grippers HGRT, heavy-duty

Technical data


FESTO

Dimensions

Download CAD data → www.festo.com



HGRT-32 ... 50



- 1 Supply port, opening
- 2 Supply port, closing
- 3 Alternative supply port, sealed on delivery
- 4 Sealing air, sealed on delivery

- 5 Sensor slot for proximity sensor
- 6 O-ring for radial gripper
HGRT-16 ... 25: Ø 3x1.5
HGRT-32 ... 50: Ø 5x1.5
- 7 Centring sleeves ZBH
(4 included in the scope of delivery)

Radial grippers HGRT, heavy-duty

Technical data

FESTO

Size	B1	B2 ¹⁾	B3	B4	B5	B6	D1 Ø	D2 Ø	D3 Ø	D4 Ø	D5	D6	D7	D8	D9 Ø
[mm]	±0.05		±0.1	+0.05	±0.1	±0.05	H8	+0.1	H8						
16	20	13	5	0.2	5	7.5	5	4.9	5	2.6	M3	M6	–	M3	3.2
20	28	18	6	0.2	6	10	7	7.4	7	4.2	M5	M6	M3	M5	5.3
25	35	23	7	0.2	7	12.5	9	9.4	9	5.1	M6	M8	M5	M6	6.4
32	40	27	10	0.2	10	14.5	9	9.4	9	5.1	M6	M8	M5	M6	6.4
40	50	33	11	0.2	11	18	12	10.4	12	6.8	M8	M8	M5	M8	10.3
50	64	42	14	0.2	14	22.5	15	13.5	15	8.5	M10	M12	M5	M10	12.4

Size	D10	D12	EE	E1	E2	E3	H1		H2		H3	H4		H5	
							±0.05	-G ±0.05	±0.05	-G ±0.05		±0.1	-G ±0.1	±0.1	-G ±0.1
[mm]		+0.2													
16	–	6	M3	M3	M3	M3	69	77.5	56.5	65	26.5	31	39.5	28	36.5
20	–	6	M5	M3	M3	M3	88.5	97.5	71	80	35.1	39	48	34.5	43.5
25	M3	6	M5	M3	M3	M3	109	120	88	99	42.5	48.3	59.3	42.5	53.5
32	M3	8	M5	M5	M5	M5	125	137	102	114	49	54.7	66.7	49	61
40	M3	8	G ¹ / ₈	M5	G ¹ / ₈	M5	154.6	172.6	122	140	63.6	65.5	83.5	58	76
50	M3	8	G ¹ / ₈	M5	G ¹ / ₈	M5	193.5	215.5	153	175	79.5	82.4	104.4	73	95

Size	H6		H7		H8		H9		H10		H11		H12	H13 ¹⁾
	±0.1	-G ±0.1	±0.1	-G ±0.1		-G	±0.1	-G ±0.1	±0.1	-G ±0.1	±0.1	-G ±0.1		
[mm]														
16	13	13	–	–	–	–	–	–	–	–	24.5	33	5.3	9
20	16	16	–	–	52.5	61.5	–	–	–	–	29	38	6	12
25	19.5	19.5	–	–	65.5	76.5	28	39	36	47	36	47	7.6	14
32	20	20	35.5	46.5	75.5	87.5	34.5	46.5	42.5	54.5	42.4	54.2	8.1	16
40	26	29	45	56.5	90	108	47	65	55	73	48	64.5	9.7	20
50	32	32	56	70	113	135	72	94	80	102	62	80	13.5	25

Size	H14 ¹⁾	H15	L1	L2	L3	L4 ¹⁾	L5	L6	L8	L9 ¹⁾	L10	L11	L12	T1
[mm]		–0.3	±0.05		+0.1		±0.05	±0.5	±0.1		±0.1	±0.1		+0.1
16	4	1.2	38.3	21±0.1	14	27	6.5	39	23	27	–	34	–	1.3
20	5	1.4	49.9	30±0.1	17	34	9	50.4	30	34	–	44	11	1.6
25	6	1.9	61.1	39±0.1	22	42	11	61.2	39	41	33	54	11	2.1
32	7	1.9	72.2	22.5 ^{+0.1}	24	51	12	72.2	22.5	48	41	64	11	2.1
40	9	2.4	90.3	28 ^{+0.1}	32	63	16.5	90.8	28	62	47	80	11	2.6
50	11	2.9	113.2	35 ^{+0.1}	36	80	20	113	35	78	59	100	11	3.1


Size	T2		T3	T4	T5	T6	T7	T8	T9	T10	T11	T12	T13	W1	W2
	min.	-G min.													
[mm]			min.	min.			+0.1	+0.1	min.	min.	min.	min.	+0.1	±2°	+3°
16	5	5	4	4	4	–	3.1	1.3	5	4	–	–	1.2	90	1
20	8.5	8	5	4	5	4.3	4.1	1.6	8	4	–	4	1.2	90	1
25	10	10	5	4.5	6	5.8	5.1	2.1	10	4.5	5.5	–	1.2	90	1
32	9.5	9.5	5	5	7	6.3	5.2	2.1	9.5	5	5.5	–	1.2	90	1
40	14.5	14.5	8.5	5	8	7.8	6.2	2.6	12.5	8.5	5.5	–	1.2	90	1
50	15	15	8.5	5	10	10.55	8.1	3.1	15	8.5	5.5	–	1.2	90	1

1) Tolerance for centring hole ±0.02 mm
Tolerance for thread ±0.1 mm

Radial grippers HGRT, heavy-duty

Technical data

FESTO

Ordering data				
	Size	Double-acting without compression spring		Single-acting or with gripping force retention, closing
	[mm]	Part No.	Type	Part No. Type
	16	563904	HGRT-16-A	563905 HGRT-16-A-G2
	20	563906	HGRT-20-A	563907 HGRT-20-A-G2
	25	563908	HGRT-25-A	563909 HGRT-25-A-G2
	32	563910	HGRT-32-A	563911 HGRT-32-A-G2
	40	563912	HGRT-40-A	563913 HGRT-40-A-G2
	50	563914	HGRT-50-A	563915 HGRT-50-A-G2

Ordering data – Wearing parts kits		
Size	Part No.	Type
[mm]		
16	1459481	HGRT-16
20	1459482	HGRT-20
25	1459483	HGRT-25
32	1459484	HGRT-32
40	1459485	HGRT-40
50	1459486	HGRT-50


Radial grippers HGRT








Accessories

FESTO

Adapter kit
HMSV, HAPG, DHAA

Material:
Wrought aluminium alloy
Free of copper and PTFE
RoHS-compliant

 Note
The kit includes the individual mounting interface as well as the necessary mounting material.

Permissible drive/gripper combinations with adapter kit					Download CAD data → www.festo.com		
Combination	Drive Size	Gripper Size	Mounting option		Adapter kit		
					CRC ¹⁾	Part No.	Type
DGSL/HGRT	DGSL	HGRT					
	8, 10	16	■	■	2	1273902	DHAA-G-G6-8-B11-16
	12, 16	16	■	■		1467524	DHAA-G-G6-12-B11-16
	12, 16	20	■	■		1278364	DHAA-G-G6-12-B11-20
	20, 25	25	■	■		1468307	DHAA-G-G6-20-B11-25
	25	32	■	■		1280494	DHAA-G-G6-25-B11-32
SLT/HGRT	SLT	HGRT					
	10	16	■	–	2	1274402	DHAA-G-G3-10-B11-16
	16	20	■	–		1278980	DHAA-G-G3-16-B11-20
	20	25	■	–		1279954	DHAA-G-G3-20-B11-25
	25	32	■	–		1280734	DHAA-G-G3-25-B11-32
	25	40	■	–		1281448	DHAA-G-G3-25-B11-40
HMP/HGRT	HMP	HGRT					
	16	25	–	■	2	1279797	DHAA-G-H2-16-B11-25
	20	32	–	■		1280562	DHAA-G-H2-20-B11-32
	25	32	–	■		1471637	DHAA-G-H2-25-B11-32
	20	40	–	■		1281049	DHAA-G-H2-20-B11-40
	25	40	–	■		1472239	DHAA-G-H2-25-B11-40
DRQD/HGRT	DRQD	HGRT					
	16	16	■	■	2	1273999	DHAA-G-Q5-16-B11-16
	20	20	■	■		1465263	DHAA-G-Q5-20-B11-20
	25, 32	25	■	■		1279439	DHAA-G-Q5-25-B11-25
	25, 32 ²⁾	25	■	■		1468974	DHAA-G-Q5-25-E-B11-25
	25, 32	32	■	■		1468949	DHAA-G-Q5-25-B11-32
	25, 32 ²⁾	32	■	■		1468980	DHAA-G-Q5-25-E-B11-32
	32	40	■	■		1280996	DHAA-G-Q5-32-B11-40
DRRD/HGRT	DRRD	HGRT					
	16	16	■	■	2	2185606	DHAA-G-Q11-16-B11-16
	20	20	■	■		2184467	DHAA-G-Q11-20-B11-20
	25	25	■	■		1741183	DHAA-G-Q11-25-B11-25
	25	32	■	■		1743177	DHAA-G-Q11-25-B11-32
	32	25	■	■		2184080	DHAA-G-Q11-32-B11-25
	32	32	■	■		2184322	DHAA-G-Q11-32-B11-32
	32	40	■	■		2184652	DHAA-G-Q11-32-B11-40
	35	40	■	■		2185436	DHAA-G-Q11-35-B11-40

1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

2) In combination with DRQD-...-E444 (flanged shaft with energy through-feed).


Radial grippers HGRT







Accessories

FESTO

Adapter kit
HMSV, HAPG, DHAA

Material:
Wrought aluminium alloy
Free of copper and PTFE
RoHS-compliant

 Note
The kit includes the individual mounting interface as well as the necessary mounting material.

Permissible drive/gripper combinations with adapter kit					Download CAD data → www.festo.com		
Combination	Drive Size	Gripper			Adapter kit		
		Size	Mounting option		CRC ¹⁾	Part No.	Type
							
HSP/HGRT	HSP	HGRT			DHAA		
	16	16	■	—	2	1274347	DHAA-G-H4-16-B11-16
						540882	HAPG-71-B
	25	16	■	—		1274347	DHAA-G-H4-16-B11-16
						540883	HAPG-72-B
HSW/HGRT	HSW	HGRT			DHAA		
	12, 16	16	■	—	2	1274347	DHAA-G-H4-16-B11-16
						540882	HAPG-71-B
EGSL/HGRT	EGSL	HGRT			DHAA		
	45, 55	20	■	■	2	1278364	DHAA-G-G6-12-B11-20
	45, 55	25	■	■		1279418	DHAA-G-E8-45-B11-25
	75	25	■	■		1468307	DHAA-G-G6-20-B11-25
	75	32	■	■		1280494	DHAA-G-G6-25-B11-32
EGSA/HGRT	EGSA	HGRT			DHAA		
	50	16	■	■	2	1467524	DHAA-G-G6-12-B11-16
						560017	HMSV-61
	50	20	■	■		1278364	DHAA-G-G6-12-B11-20
						560017	HMSV-61
	50	25	■	■		1468307	DHAA-G-G6-20-B11-25
						560017	HMSV-61
	60	25	■	■		1468307	DHAA-G-G6-20-B11-25
						560018	HMSV-62
	60	32	■	■	1280494	DHAA-G-G6-25-B11-32	
					560018	HMSV-62	

1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.


Radial grippers HGRT




Accessories

FESTO

Adapter kit
HMSV, HAPG, DHAA

Material:
Wrought aluminium alloy
Free of copper and PTFE
RoHS-compliant

 **Note**
The kit includes the individual mounting interface as well as the necessary mounting material.

Permissible drive/gripper combinations with adapter kit					Download CAD data → www.festo.com	
Combination	Drive Size	Gripper Size	Mounting option		CRC ¹⁾	Part No. Type
						
ERMB/HGRT	ERMB	HGRT				
	20	20	■	■	2	1465263 DHAA-G-Q5-20-B11-20
	25, 32	25	■	■		1279439 DHAA-G-Q5-25-B11-25
	25, 32	32	■	■		1468949 DHAA-G-Q5-25-B11-32

1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Radial grippers HGRT

Accessories


FESTO

Stroke reducing kit HGRT-HR

Materials:

Screw: Steel

Lock nut: Case-hardened steel




Dimensions and ordering data									
For size [mm]	D1	L1	T5	⌀ 1	⌀ 2	Adjustable end-position range [mm]	Weight [g]	Part No.	Type
16	M6	26	4	10	3	20	7	564296	HGRT-HR-16
20	M6	31	5	10	3	25	9	564297	HGRT-HR-20
25	M8	36	6	13	4	30	18	564298	HGRT-HR-25
32	M8	41	7	13	4	35	20	564299	HGRT-HR-32
40	M8	51	8	13	4	45	24	564300	HGRT-HR-40
50	M12	61	10	19	6	50	66	564301	HGRT-HR-50

Sensor bracket DASI


Material:

DASI-B10-25-S8: Polyamide


DASI-B10-40-S12: Aluminium



DASI-B10-25-S8



DASI-B10-40-S12




Dimensions and ordering data				
For type	H1 ±0.02	H2 ±0.1	L1 ±0.01	L2
HGRT-25-A	66.5	28	45	33
HGRT-25-A-G2	77.5	39	45	33
HGRT-32-A	76	34.5	53	64
HGRT-32-A-G2	88	46.5	53	64
HGRT-40-A	91	47	67	47
HGRT-40-A-G2	109	65	67	47
HGRT-50-A	114	72	84	59
HGRT-50-A-G2	136	94	84	59

For size [mm]	B1	B2	H3 ±0.1	H4	H5	L3 ±0.1	L4	L5	L6 ±0.2	Weight [g]	Part No.	Type
25, 32	8.45	12	8	11.5	16	12	5.5	6	20	39	564311	DASI-B10-25-S8
40, 50	10.5	16	8	18	16	—	—	8	20	18	564312	DASI-B10-40-S12


Radial grippers HGRT


Accessories


FESTO


Ordering data – Centring sleeves				Technical data → Internet: zbh
	For size [mm]	Part No.	Type	PU ¹⁾
	16	189652	ZBH-5	10
	20	186717	ZBH-7	
	25, 32	150927	ZBH-9	
	40	189653	ZBH-12	
	50	191409	ZBH-15	

1) Packaging unit

Proximity sensor for size 16 ... 32							Technical data → Internet: smt
Ordering data – Proximity sensors for C-slot, magneto-resistive							
	Type of mounting	Electrical connection, connection direction	Switching output	Cable length [m]	Part No.	Type	
N/O contact							
	Insertable in the slot lengthwise	Cable, 3-wire, lateral	PNP	2.5	547862	SMT-10G-PS-24V-E-2,5Q-OE	
		Plug M8x1, 3-pin, lateral		0.3	547863	SMT-10G-PS-24V-E-0,3Q-M8D	

Proximity sensor for size 40 ... 50							Technical data → Internet: smt
Ordering data – Proximity sensors for T-slot, magneto-resistive							
	Type of mounting	Electrical connection, connection direction	Switching output	Cable length [m]	Part No.	Type	
N/O contact							
	Insertable in the slot lengthwise	Cable, 3-wire, lateral	PNP	2.5	547859	SMT-8G-PS-24V-E-2,5Q-OE	
		Plug M8x1, 3-pin, lateral		0.3	547860	SMT-8G-PS-24V-E-0,3Q-M8D	

Proximity sensor for size 40							Technical data → Internet: smat
Ordering data – Position transmitters for T-slot							
	Type of mounting	Electrical connection, connection direction	Analogue output [V]	Cable length [m]	Part No.	Type	
	Insertable in the slot from above	Plug M8x1, 3-pin, lateral	0 ... 10	0.3	553744	SMAT-8M-U-E-0,3-M8D	


 Note



Mode of operation:
The position transmitter continuously senses the position of the piston. It has an analogue output with an output signal in proportion to the piston position.

Radial grippers HGRT

Accessories

FESTO

Ordering data – Proximity sensors, inductive, for sensor bracket DASI					Technical data → Internet: sien	
	Thread	Contact	Connection	Part No.	Type	
	For DASI-B10-25-S8					
	M8	N/O contact	Cable, 2.5 m	150386	SIEN-M8B-PS-K-L	
			Plug	150387	SIEN-M8B-PS-S-L	
	For DASI-B10-40-S12					
	M12	N/O contact	Cable, 2.5 m	150402	SIEN-M12B-PS-K-L	
			Plug	150403	SIEN-M12B-PS-S-L	

Ordering data – Connecting cables				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541333	NEBU-M8G3-K-2.5-LE3
			5	541334	NEBU-M8G3-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541338	NEBU-M8W3-K-2.5-LE3
			5	541341	NEBU-M8W3-K-5-LE3

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com