








Filters MS-LF/LFM/LFX, MS series



# Filters MS-LF/LFM/LFX, MS series



Product range overview – MS series service units

Type	Size	Pneumatic connection in housing	Connecting plate	Pressure regulation range [bar]						Grade of filtration [µm]			
				0.05 ...	0.05 ...	0.1 ...	0.3 ...	0.1 ...	0.5 ...	0.01	1	5	40
Code			AG...	D2	D4	D5	D6	D7	D8	A	B	C	E
<b>Service units</b>													
<b>MSB-FRC</b> 	4	G1/8, G1/4	G1/8, G1/4, G3/8	-	-	-	■	■	-	-	-	■	■
	6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	-	-	-	■	■	-	-	-	■	■
	9	-	-	-	-	-	-	-	-	-	-	-	-
	12	-	-	-	-	-	-	-	-	-	-	-	-
<b>Service unit combinations (further variants can be ordered using the configurator → Internet: msb4, msb6 or msb9)</b>													
<b>MSB</b> 	4	G1/4	G1/8, G1/4, G3/8	-	-	-	■	■	-	-	-	■	■
	6	G1/2	G1/4, G3/8, G1/2, G3/4	-	-	-	■	■	-	-	-	■	■
	9	-	-	-	-	-	-	-	-	-	-	-	-
	12	-	-	-	-	-	-	-	-	-	-	-	-
<b>Individual devices</b>													
Filter regulators <b>MS-LFR</b> 	4	G1/8, G1/4	G1/8, G1/4, G3/8	-	-	■	■	■	-	-	-	■	■
	6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	-	-	■	■	■	■	-	-	■	■
	9	G3/4, G1	G1/2, G3/4, G1, G1 1/4, G1 1/2	-	-	■	■	■	■	-	-	■	■
	12	-	G1, G1 1/4, G1 1/2, G2	-	-	-	■	■	■	-	-	■	■
Filters <b>MS-LF</b> 	4	G1/8, G1/4	G1/8, G1/4, G3/8	-	-	-	-	-	-	-	-	■	■
	6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	-	-	-	-	-	-	-	-	■	■
	9	G3/4, G1	G1/2, G3/4, G1, G1 1/4, G1 1/2	-	-	-	-	-	-	-	-	■	■
	12	-	G1, G1 1/4, G1 1/2, G2	-	-	-	-	-	-	-	-	■	■
Fine and micro filters <b>MS-LFM</b> 	4	G1/8, G1/4	G1/8, G1/4, G3/8	-	-	-	-	-	-	■	■	-	-
	6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	-	-	-	-	-	-	■	■	-	-
	9	G3/4, G1	G1/2, G3/4, G1, G1 1/4, G1 1/2	-	-	-	-	-	-	■	■	-	-
	12	-	G1, G1 1/4, G1 1/2, G2	-	-	-	-	-	-	■	■	-	-
Activated carbon filters <b>MS-LFX</b> 	4	G1/8, G1/4	G1/8, G1/4, G3/8	-	-	-	-	-	-	-	-	-	-
	6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	-	-	-	-	-	-	-	-	-	-
	9	G3/4, G1	G1/2, G3/4, G1, G1 1/4, G1 1/2	-	-	-	-	-	-	-	-	-	-
	12	-	G1, G1 1/4, G1 1/2, G2	-	-	-	-	-	-	-	-	-	-
Water separators <b>MS-LWS</b> 	4	-	-	-	-	-	-	-	-	-	-	-	-
	6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	-	-	-	-	-	-	-	-	-	-
	9	G3/4, G1	G1/2, G3/4, G1, G1 1/4, G1 1/2	-	-	-	-	-	-	-	-	-	-
	12	-	G1, G1 1/4, G1 1/2, G2	-	-	-	-	-	-	-	-	-	-

# Filters MS-LF/LFM/LFX, MS series

Product range overview – MS series service units



Type	Size	Bowl guard		Condensate drains				Pressure indicator					Security		Options		→ Page/ Internet
		Plastic bowl with plastic bowl guard	Metal bowl	Manual rotary	Semi-automatic	Fully automatic	External, fully automatic, electrical	Cover plate (without pressure gauge)	Integrated MS pressure gauge	Adapter plate for EN pressure gauge G1/8	Adapter plate for EN pressure gauge G1/4	Pressure sensor	Rotary knob with detent, lockable via accessories	Rotary knob with integrated lock	Silencer	Flow direction from right to left	
Code		R	U	M	H	V	E...	VS	AG	A8	A4	AD...	AS	E11	S	Z	
<b>Service units</b>																	
<b>MSB-FRC</b>	4	■	-	■	-	■	-	-	■	-	-	-	■	-	-	■	msb4
	6	■	■	■	-	■	-	-	■	-	-	-	■	-	-	■	msb6
	9	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	12	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
<b>Service unit combinations</b>																	
<b>MSB</b>	4	■	■	■	-	■	-	-	■	-	-	-	■	-	-	■	msb4
	6	■	■	■	-	■	-	-	■	-	-	-	■	-	-	■	msb6
	9	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	12	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
<b>Individual devices</b>																	
Filter regulators <b>MS-LFR</b>	4	■	■	■	■	■	-	■	■	■	■	■	■	■	-	■	ms4-lfr
	6	■	■	■	■	■	■	■	■	-	■	■	■	■	-	■	ms6-lfr
	9	-	■	■	■	■	■	■	■	-	■	■	■	■	-	■	ms9-lfr
	12	-	■	■	-	■	■	■	■	-	■	-	■	■	-	■	ms12-lfr
Filters <b>MS-LF</b>	4	■	■	■	■	■	-	-	-	-	-	-	-	-	-	■	8, 10
	6	■	■	■	■	■	■	-	-	-	-	-	-	-	-	■	8, 10
	9	-	■	■	■	■	■	-	-	-	-	-	-	-	-	■	36
	12	-	■	■	-	■	■	-	-	-	-	-	-	-	-	■	65
Fine and micro filters <b>MS-LFM</b>	4	■	■	■	■	■	-	-	-	-	-	-	-	-	-	■	8, 18
	6	■	■	■	■	■	■	-	-	-	-	-	-	-	-	■	8, 18
	9	-	■	■	■	■	■	-	-	-	-	-	-	-	-	■	44
	12	-	■	■	-	■	■	-	-	-	-	-	-	-	-	■	72
Activated carbon filters <b>MS-LFX</b>	4	■	■	-	-	-	-	-	-	-	-	-	-	-	-	■	8, 30
	6	■	■	-	-	-	-	-	-	-	-	-	-	-	-	■	8, 30
	9	-	■	-	-	-	-	-	-	-	-	-	-	-	-	■	58
	12	-	■	-	-	-	-	-	-	-	-	-	-	-	-	■	81
Water separators <b>MS-LWS</b>	4	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
	6	-	■	-	-	■	■	-	-	-	-	-	-	-	-	■	ms6-lws
	9	-	■	-	-	■	■	-	-	-	-	-	-	-	-	■	ms9-lws
	12	-	■	-	-	■	■	-	-	-	-	-	-	-	-	■	ms12-lws

# Filters MS-LF/LFM/LFX, MS series

Product range overview – MS series service units



Type	Size	Pneumatic connection in housing	Connecting plate	Pressure regulation range [bar]						Supply voltage			
				0.05 ... 0.7	0.05 ... 2.5	0.1 ... 4	0.3 ... 7	0.1 ... 12	0.5 ... 16	24 V DC, connection pattern to EN 175301	24 V DC, connection M12 to IEC 61076-2-101	110 V AC, connection pattern to EN 175301	230 V AC, connection pattern to EN 175301
Code			AG...	D2	D4	D5	D6	D7	D8	V24	V24P	V110	V230
<b>Individual devices</b>													
Pressure regulators <b>MS-LR</b>		4	G1/8, G1/4	G1/8, G1/4, G3/8	-	-	■	■	■	-	-	-	-
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	-	-	■	■	■	■	-	-	-
		9	G3/4, G1	G1/2, G3/4, G1, G1 1/4, G1 1/2	-	-	■	■	■	■	-	-	-
		12	-	G1, G1 1/4, G1 1/2, G2	-	-	-	■	■	■	-	-	-
Pressure regulators <b>MS-LRB</b>		4	G1/4	G1/8, G1/4, G3/8	-	-	■	■	■	-	-	-	-
		6	G1/2	G1/4, G3/8, G1/2, G3/4	-	-	■	■	■	■	-	-	-
		9	-	-	-	-	-	-	-	-	-	-	-
		12	-	-	-	-	-	-	-	-	-	-	-
Precision pressure regulators <b>MS-LRP</b>		4	-	-	-	-	-	-	-	-	-	-	-
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	■	■	■	-	■	-	-	-	-
		9	-	-	-	-	-	-	-	-	-	-	-
		12	-	-	-	-	-	-	-	-	-	-	-
Precision pressure regulators <b>MS-LRPB</b>		4	-	-	-	-	-	-	-	-	-	-	-
		6	G1/2	G1/4, G3/8, G1/2, G3/4	■	■	■	-	■	-	-	-	-
		9	-	-	-	-	-	-	-	-	-	-	-
		12	-	-	-	-	-	-	-	-	-	-	-
Electrical pressure regulators <b>MS-LRE</b>		4	-	-	-	-	-	-	-	-	-	-	-
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	-	-	■	■	■	■	-	-	-
		9	-	-	-	-	-	-	-	-	-	-	-
		12	-	-	-	-	-	-	-	-	-	-	-
Lubricators <b>MS-LOE</b>		4	G1/8, G1/4	G1/8, G1/4, G3/8	-	-	-	-	-	-	-	-	-
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	-	-	-	-	-	-	-	-	-
		9	G3/4, G1	G1/2, G3/4, G1, G1 1/4, G1 1/2	-	-	-	-	-	-	-	-	-
		12	-	G1, G1 1/4, G1 1/2, G2	-	-	-	-	-	-	-	-	-
On-off valves, manually actuated <b>MS-EM(1)</b>		4	G1/8, G1/4	G1/8, G1/4, G3/8	-	-	-	-	-	-	-	-	-
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	-	-	-	-	-	-	-	-	-
		9	G3/4, G1	G1/2, G3/4, G1, G1 1/4, G1 1/2	-	-	-	-	-	-	-	-	-
		12	-	G1, G1 1/4, G1 1/2, G2	-	-	-	-	-	-	-	-	-
On-off valves, electrically actuated <b>MS-EE</b>		4	G1/8, G1/4	G1/8, G1/4, G3/8	-	-	-	-	-	■	-	■	■
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	-	-	-	-	-	■	-	■	■
		9	G3/4, G1	G1/2, G3/4, G1, G1 1/4, G1 1/2	-	-	-	-	-	■	■	■	■
		12	-	G1, G1 1/4, G1 1/2, G2	-	-	-	-	-	■	■	■	■
Soft-start valves, pneumatically actuated <b>MS-DL</b>		4	G1/8, G1/4	G1/8, G1/4, G3/8	-	-	-	-	-	-	-	-	-
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	-	-	-	-	-	-	-	-	-
		9	-	-	-	-	-	-	-	-	-	-	-
		12	-	G1, G1 1/4, G1 1/2, G2	-	-	-	-	-	-	-	-	-
Soft-start valves, electrically actuated <b>MS-DE</b>		4	G1/8, G1/4	G1/8, G1/4, G3/8	-	-	-	-	-	■	-	■	■
		6	G1/4, G3/8, G1/2	G1/4, G3/8, G1/2, G3/4	-	-	-	-	-	■	-	■	■
		9	-	-	-	-	-	-	-	-	-	-	-
		12	-	G1, G1 1/4, G1 1/2, G2	-	-	-	-	-	■	■	■	■

# Filters MS-LF/LFM/LFX, MS series

Product range overview – MS series service units



Type	Size	Bowl guard		Pressure indicator				Security			Options		→ Page/ Internet
		Plastic bowl with plastic bowl guard	Metal bowl	Cover plate (without pressure gauge)	Integrated MS pressure gauge	Adapter plate for EN pressure gauge G1/8	Adapter plate for EN pressure gauge G1/4	Pressure sensor	Rotary knob with detent, lockable via accessories	Rotary knob with integrated lock	Silencer	Flow direction from right to left	
Code		R	U	VS	AG	A8	A4	AD...	AS	E11	S	Z	
<b>Individual devices</b>													
Pressure regulators <b>MS-LR</b>	4	-	-	■	■	■	■	■	■	■	-	■	ms4-lr
	6	-	-	■	■	-	■	■	■	■	-	■	ms6-lr
	9	-	-	■	■	-	■	■	■	■	-	■	ms9-lr
	12	-	-	■	■	-	■	-	■	■	-	■	ms12-lr
Pressure regulators <b>MS-LRB</b>	4	-	-	■	■	■	■	■	■	■	-	■	ms4-lrb
	6	-	-	■	■	-	■	■	■	■	-	■	ms6-lrb
	9	-	-	-	-	-	-	-	-	-	-	-	-
	12	-	-	-	-	-	-	-	-	-	-	-	-
Precision pressure regulators <b>MS-LRP</b>	4	-	-	-	-	-	-	-	-	-	-	-	-
	6	-	-	■	-	■	■	■	■	■	-	■	ms6-lrp
	9	-	-	-	-	-	-	-	-	-	-	-	-
	12	-	-	-	-	-	-	-	-	-	-	-	-
Precision pressure regulators <b>MS-LRPB</b>	4	-	-	-	-	-	-	-	-	-	-	-	-
	6	-	-	■	-	■	■	■	■	■	-	■	ms6-lrpb
	9	-	-	-	-	-	-	-	-	-	-	-	-
	12	-	-	-	-	-	-	-	-	-	-	-	-
Electrical pressure regulators <b>MS-LRE</b>	4	-	-	-	-	-	-	-	-	-	-	-	-
	6	-	-	■	■	-	■	-	-	-	-	■	ms6-lre
	9	-	-	-	-	-	-	-	-	-	-	-	-
	12	-	-	-	-	-	-	-	-	-	-	-	-
Lubricators <b>MS-LOE</b>	4	■	■	-	-	-	-	-	-	-	-	■	ms4-loe
	6	■	■	-	-	-	-	-	-	-	-	■	ms6-loe
	9	-	■	-	-	-	-	-	-	-	-	■	ms9-loe
	12	-	■	-	-	-	-	-	-	-	-	■	ms12-loe
On-off valves, manually actuated <b>MS-EM(1)</b>	4	-	-	■	■	■	■	■	-	-	■	■	ms4-em1
	6	-	-	■	■	-	■	■	-	-	■	■	ms6-em1
	9	-	-	■	■	-	■	-	-	-	■	■	ms9-em
	12	-	-	■	■	-	■	-	-	-	■	■	ms12-em
On-off valves, electrically actuated <b>MS-EE</b>	4	-	-	■	■	■	■	■	-	-	■	■	ms4-ee
	6	-	-	■	■	-	■	■	-	-	■	■	ms6-ee
	9	-	-	■	■	-	■	-	-	-	■	■	ms9-ee
	12	-	-	■	■	-	■	-	-	-	■	■	ms12-ee
Soft-start valves, pneumatically actuated <b>MS-DL</b>	4	-	-	■	■	■	■	■	-	-	-	■	ms4-dl
	6	-	-	■	■	-	■	■	-	-	-	■	ms6-dl
	9	-	-	-	-	-	-	-	-	-	-	-	-
	12	-	-	■	■	-	■	-	-	-	-	■	ms12-dl
Soft-start valves, electrically actuated <b>MS-DE</b>	4	-	-	■	■	■	■	■	-	-	-	■	ms4-de
	6	-	-	■	■	-	■	■	-	-	-	■	ms6-de
	9	-	-	-	-	-	-	-	-	-	-	-	-
	12	-	-	■	■	-	■	-	-	-	-	■	ms12-de

# Filters MS-LF/LFM/LFX, MS series

Product range overview – MS series service units



Type	Size	Pneumatic connection in housing	Connecting plate	Performance Level		Supply voltage				
				Category 1, 1-channel	Category 4, 2-channel with self-monitoring	24 V DC, connection pattern to EN 175301	24 V DC, connection M12 to IEC 61076-2-101/ to EN 60947-5-2	110 V AC, connection pattern to EN 175301	230 V AC, connection pattern to EN 175301	
Code			AG...	C	E	V24	V24P	V110	V230	
<b>Individual devices</b>										
Soft start and exhaust valves <b>MS-SV-C</b>		4	–							
		6	G $\frac{1}{2}$	G $\frac{1}{4}$ , G $\frac{3}{8}$ , G $\frac{1}{2}$ , G $\frac{3}{4}$	■	–	■	■	■	■
		9	G $\frac{3}{4}$ , G1	G $\frac{1}{2}$ , G $\frac{3}{4}$ , G1, G1 $\frac{1}{4}$ , G1 $\frac{1}{2}$	■	–	■	■	■	■
		12	–							
Soft start and exhaust valves <b>MS-SV-E</b>		4	–							
		6	G $\frac{1}{2}$	G $\frac{1}{4}$ , G $\frac{3}{8}$ , G $\frac{1}{2}$ , G $\frac{3}{4}$	–	■	■	–	–	–
		9	–							
		12	–							
Membrane air dryers <b>MS-LDM1</b>		4	G $\frac{1}{8}$ , G $\frac{1}{4}$	G $\frac{1}{8}$ , G $\frac{1}{4}$ , G $\frac{3}{8}$	–	–	–	–	–	–
		6	G $\frac{1}{4}$ , G $\frac{3}{8}$ , G $\frac{1}{2}$	G $\frac{1}{4}$ , G $\frac{3}{8}$ , G $\frac{1}{2}$ , G $\frac{3}{4}$	–	–	–	–	–	–
		9	–							
		12	–							
Branching modules <b>MS-FRM</b>		4	G $\frac{1}{8}$ , G $\frac{1}{4}$	G $\frac{1}{8}$ , G $\frac{1}{4}$ , G $\frac{3}{8}$	–	–	–	–	–	–
		6	G $\frac{1}{4}$ , G $\frac{3}{8}$ , G $\frac{1}{2}$	G $\frac{1}{4}$ , G $\frac{3}{8}$ , G $\frac{1}{2}$ , G $\frac{3}{4}$	–	–	–	–	–	–
		9	G $\frac{3}{4}$ , G1	G $\frac{1}{2}$ , G $\frac{3}{4}$ , G1, G1 $\frac{1}{4}$ , G1 $\frac{1}{2}$	–	–	–	–	–	–
		12	–	G1, G1 $\frac{1}{4}$ , G1 $\frac{1}{2}$ , G2	–	–	–	–	–	–
Distributor blocks <b>MS-FRM-FRZ</b>		4	G $\frac{1}{4}$	–	–	–	–	–	–	
		6	G $\frac{1}{2}$	–	–	–	–	–	–	
		9	–							
		12	–							
Flow sensors <b>SFAM</b>		4	–							
		6	G $\frac{1}{2}$	G $\frac{1}{2}$	–	–	–	–	–	–
		9	–	G1, G1 $\frac{1}{2}$	–	–	–	–	–	–
		12	–							

# Filters MS-LF/LFM/LFX, MS series


Product range overview – MS series service units



Type	Size	Bowl guard		Pressure indicator					Switch output		Options		→ Page/ Internet
		Plastic bowl with plastic bowl guard	Metal bowl	Cover plate (without pressure gauge)	Integrated MS pressure gauge	Adapter plate for EN pressure gauge G1/8	Adapter plate for EN pressure gauge G1/4	Pressure sensor	2x PNP or NPN, 1 analogue output 4 ... 20 mA	2x PNP or NPN, 1 analogue output 0 ... 10 V	Silencer	Flow direction from right to left	
Code		R	U	VS	AG	A8	A4	AD...	2SA	2SV	S	Z/R	
<b>Individual devices</b>													
Soft start and exhaust valves <b>MS-SV-C</b>	4	-											-
	6	-	-	■	■	-	■	■	-	-	■	■	ms6-sv
	9	-	-	■	■	-	■	■	-	-	■	■	ms9-sv
	12	-											-
Soft start and exhaust valves <b>MS-SV-E</b>	4	-											-
	6	-	-	■	■	-	■	■	-	-	■	■	ms6-sv
	9	-											-
	12	-											-
Membrane air dryers <b>MS-LDM1</b>	4	-	■	-	-	-	-	-	-	-	-	■	ms4-ldm1
	6	-	■	-	-	-	-	-	-	-	-	■	ms6-ldm1
	9	-											-
	12	-											-
Branching modules <b>MS-FRM</b>	4	-	-	■	■	■	■	■	-	-	-	■	ms4-frm
	6	-	-	■	■	-	■	■	-	-	-	■	ms6-frm
	9	-	-	■	■	-	■	■	-	-	-	■	ms9-frm
	12	-	-	■	-	-	-	-	-	-	-	-	ms12-frm
Distributor blocks <b>MS-FRM-FRZ</b>	4	-	-	-	-	-	-	-	-	-	-	■	ms4-frm
	6	-	-	-	-	-	-	-	-	-	-	■	ms6-frm
	9	-											-
	12	-											-
Flow sensors <b>SFAM</b>	4	-											-
	6	-	-	-	-	-	-	-	■	■	-	■	sfam-62
	9	-	-	-	-	-	-	-	■	■	-	■	sfam-90
	12	-											-

# Filters MS4/MS6-LF/LFM/LFX, MS series

Peripherals overview



### Note

Other accessories:

- Module connector for combination with sizes MS4/MS6 or size MS9 → Internet: amv, rmv, armv
- Adapter plate for mounting on profiles → Internet: ipm-80, ipm-40-80, ipm-80-80

Mounting attachments and accessories						
		Individual device		Combination		→ Page/Internet
		without connecting plate	with connecting plate	without connecting plate	with connecting plate	
1	Cover plate MS4/6-END	■	-	■	-	ms4-end, ms6-end
2	Connecting plate MS4/6-AG...	-	■	-	■	ms4-ag, ms6-ag
3	Mounting bracket MS4/6-WB	■	■	-	-	ms4-wb, ms6-wb
4	Mounting bracket MS4-WBM	■	■	-	-	ms4-wbm
5	Module connector MS4/6-MV	-	■	■	■	ms4-mv, ms6-mv
6	Filter pollution indicator DP/DN/DPI/DNI	■ for LFM	■ for LFM	■ for LFM	■ for LFM	28
7	Connecting cable NEBU-M8...-LE3/NEBU-M12...-LE4	■ for LFM	■ for LFM	■ for LFM	■ for LFM	nebu
-	Mounting bracket MS4/6-WP/WPB/WPE/WPM	-	■	■	■	ms4-wp, ms6-wp



# Filters MS4/MS6-LF/LFM/LFX, MS series

Type codes

MS 6 - LFM - 1/4 - A R M - - DA

### Series

MS	Standard service unit
----	-----------------------

### Size

4	Grid dimension 40 mm
6	Grid dimension 62 mm

### Service function

LF	Filter
LFM	Fine and micro filter
LFX	Activated carbon filter

### Pneumatic connection

<b>MS4</b>	
1/8	G1/8 thread
1/4	G1/4 thread
<b>MS6</b>	
1/4	G1/4 thread
3/8	G3/8 thread
1/2	G1/2 thread

### Grade of filtration (for LF and LFM only)

A	0.01 µm
B	1 µm
C	5 µm
E	40 µm

### Bowl guard

R	Plastic bowl guard
U	Integrated as metal bowl

### Condensate drain (for LF and LFM only)

M	Manual rotary
V	Fully automatic

### Flow rate (for LFM and LFX only)

	Standard
HF	High flow rate

### Filter change sensor (for LFM only)

	Without differential pressure indicator
DA	Differential pressure indicator

### Further variants can be ordered using the modular system


Filters LF	→ 16
Fine and micro filters LFM	→ 28
Activated carbon filters LFX	→ 35

- Connecting plates
- Condensate drain
- Range of application (only for LFM and LFX)
- Filter pollution indicator (for LFM only)
- Type of mounting
- Alternative flow direction


# Filters MS4/MS6-LF, MS series

Technical data

Function  
Condensate drain  
manual rotary



semi or fully automatic



Flow rate  
1,000 ... 4,100 l/min  
Temperature range  
-10 ... +60 °C  
Pressure  
0 ... 20 bar

www.festo.com/en/  
Spare\_parts\_service



The sintered filter with centrifugal separation removes contamination, rust and condensate from the compressed air. The filter cartridges are replaceable.

- Good particle and condensate separation
- High flow rate with minimal pressure drop
- Available with manual, semi-automatic, fully automatic or fully automatic, electrically actuated condensate drain
- Choice of filter cartridges: 5 µm or 40 µm
- New filter cartridges → 87

General technical data					
Size	MS4		MS6		
Pneumatic connection 1, 2	G1/8	G1/4	G1/4	G3/8	G1/2
Design	Sintered filter with centrifugal separation				
Type of mounting	Via accessories				
	In-line installation				
Assembly position	Vertical ±5°				
Grade of filtration [µm]	5				
	40				
Air purity class at the output	Compressed air in accordance with ISO 8573-1:2010 [6:8:4] (Grade of filtration 5 µm)				
	Compressed air in accordance with ISO 8573-1:2010 [7:8:4] (Grade of filtration 40 µm)				
Bowl guard	Plastic bowl guard				
	Integrated as metal bowl				
Condensate drain	Manual rotary				
	Semi-automatic				
	Fully automatic				
	-		Fully automatic, electrical		
Max. condensate volume [cm³]	19 (with plastic bowl guard) 25 (with metal bowl)		38		

Note: This product conforms to ISO 1179-1 and ISO 228-1

Standard nominal flow rate qnN <sup>1)</sup> [l/min]					
Size	MS4		MS6		
Pneumatic connection	G1/8	G1/4	G1/4	G3/8	G1/2
Grade of filtration	5 µm	1,000	1,300	2,000	3,000
	40 µm	1,100	1,700	2,500	3,200
				3,800	4,100

1) Measured at p1 = 6 bar and Δp = 1 bar

# Filters MS4/MS6-LF, MS series

Technical data


Operating and environmental conditions							
Condensate drain	Manual rotary M		Semi-automatic H		Fully automatic V		Fully automatic, electrical E2/E3/E4
Size	MS4	MS6	MS4	MS6	MS4	MS6	MS6
Operating pressure [bar]	0 ... 14	0 ... 20	1.5 ... 12	1.5 ... 12	2 ... 12	2 ... 12	0.8 ... 16
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [--:9:--]		Compressed air in accordance with ISO 8573-1:2010 [--:9:--]		Compressed air in accordance with ISO 8573-1:2010 [7:9:--]		Compressed air in accordance with ISO 8573-1:2010 [--:9:--]
	Inert gases						
Ambient temperature [°C]	-10 ... +60		+5 ... +60		+5 ... +60		+1 ... +60
Temperature of medium [°C]	-10 ... +60		+5 ... +60		+5 ... +60		+1 ... +60
Storage temperature [°C]	-10 ... +60		-10 ... +60		-10 ... +60		+1 ... +60
Corrosion resistance CRC <sup>1)</sup>	2						

1) Corrosion resistance class 2 according to Festo standard 940 070  
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Weights [g]		
Size	MS4	MS6
Filter with plastic bowl guard R	189	600
Filter with metal bowl U	349	820
Filter with metal bowl U and fully automatic, electrically actuated condensate drain E2/E3/E4	-	1,800

## Materials

Sectional view



Filters		
1	Body	Die-cast aluminium
2	Plastic bowl guard	PC
3	Metal bowl	Wrought aluminium alloy, die-cast aluminium
		Viewing window
4	Filter element	PE
-	Seals	NBR
Note on materials		RoHS-compliant (not with variant E2, E3 or E4)
		Free of copper and PTFE

# Filters MS4/MS6-LF, MS series

Technical data





## Standard flow rate $q_n$ as a function of the differential pressure $\Delta p_{1-2}$



Grade of filtration 5  $\mu\text{m}$

Grade of filtration 40  $\mu\text{m}$



MS4-LF-1/8





MS4-LF-1/4



MS6-LF-1/4



MS6-LF-3/8



# Filters MS4/MS6-LF, MS series

Technical data





## Standard flow rate $q_n$ as a function of the differential pressure $\Delta p_{1-2}$

MS6-LF-1/2

Grade of filtration 5  $\mu\text{m}$


Grade of filtration 40  $\mu\text{m}$



## Dimensions – Basic version

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Manual rotary condensate drain



1 Installation dimensions

→ Flow direction

Type	B1	B2	B3	D1	L1		L2	L3	L5	L6	
					Bowl guard					Plastic	Metal
					Plastic	Metal					
MS4-LF-1/8	40	21	54	G1/8	142.8	159.4	29	60.5	25	17.7	17.7
MS4-LF-1/4				G1/4							
MS6-LF-1/4	62	31	76	G1/4	193	199	42	87.5	68	16	19
MS6-LF-3/8				G3/8							
MS6-LF-1/2				G1/2							

Note: This product conforms to ISO 1179-1 and ISO 228-1


# Filters MS4/MS6-LF, MS series

Technical data

**FESTO**


## Dimensions – Condensate drain Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

**Manual rotary M**




Barbed fitting for plastic tubing  
PCN-4

**Semi-automatic H**



QS fitting for plastic tubing  
PUN-6/PAN-6

**Fully automatic V**




Barbed fitting for plastic tubing  
PCN-4

Type	L6
<b>Plastic bowl guard</b>	
MS4-LF-...-M	17.7
MS6-LF-...-M	16
<b>Metal bowl</b>	
MS4-LF-...-M	17.7
MS6-LF-...-M	19

Type	L6
<b>Plastic bowl guard</b>	
MS4-LF-...-H	22.1
MS6-LF-...-H	20
<b>Metal bowl</b>	
MS4-LF-...-H	22.1
MS6-LF-...-H	23

Type	L6
<b>Plastic bowl guard</b>	
MS4-LF-...-V	20.4
MS6-LF-...-V	19
<b>Metal bowl</b>	
MS4-LF-...-V	20.4
MS6-LF-...-V	22

## Fully automatic, electrically actuated E2/E3/E4 Technical data → Internet: pwea



- Condensate drain PWEA:
- 2 Electrical connection: Screw terminal PG9
  - 3 Connection 360° rotatable for plastic tubing PUN-H-12x2

# Filters MS4/MS6-LF, MS series

Technical data

Ordering data							
Size	Condensate drain	Connection	Grade of filtration 5 µm		Grade of filtration 40 µm		
			Part No.	Type	Part No.	Type	
Plastic bowl guard							
MS4	manual rotary	G $\frac{1}{8}$	529403	MS4-LF- $\frac{1}{8}$ -CRM	529407	MS4-LF- $\frac{1}{8}$ -ERM	
		G $\frac{1}{4}$	529395	MS4-LF- $\frac{1}{4}$ -CRM	529399	MS4-LF- $\frac{1}{4}$ -ERM	
	fully automatic	G $\frac{1}{8}$	529405	MS4-LF- $\frac{1}{8}$ -CRV	529409	MS4-LF- $\frac{1}{8}$ -ERV	
		G $\frac{1}{4}$	529397	MS4-LF- $\frac{1}{4}$ -CRV	529401	MS4-LF- $\frac{1}{4}$ -ERV	
	MS6	manual rotary	G $\frac{1}{4}$	529623	MS6-LF- $\frac{1}{4}$ -CRM	529631	MS6-LF- $\frac{1}{4}$ -ERM
			G $\frac{3}{8}$	529639	MS6-LF- $\frac{3}{8}$ -CRM	529647	MS6-LF- $\frac{3}{8}$ -ERM
G $\frac{1}{2}$			529607	MS6-LF- $\frac{1}{2}$ -CRM	529615	MS6-LF- $\frac{1}{2}$ -ERM	
fully automatic		G $\frac{1}{4}$	529625	MS6-LF- $\frac{1}{4}$ -CRV	529633	MS6-LF- $\frac{1}{4}$ -ERV	
		G $\frac{3}{8}$	529641	MS6-LF- $\frac{3}{8}$ -CRV	529649	MS6-LF- $\frac{3}{8}$ -ERV	
		G $\frac{1}{2}$	529609	MS6-LF- $\frac{1}{2}$ -CRV	529617	MS6-LF- $\frac{1}{2}$ -ERV	
Integrated as metal bowl							
MS4	manual rotary	G $\frac{1}{8}$	535638	MS4-LF- $\frac{1}{8}$ -CUM	535644	MS4-LF- $\frac{1}{8}$ -EUM	
		G $\frac{1}{4}$	535654	MS4-LF- $\frac{1}{4}$ -CUM	535660	MS4-LF- $\frac{1}{4}$ -EUM	
	fully automatic	G $\frac{1}{8}$	535640	MS4-LF- $\frac{1}{8}$ -CUV	535642	MS4-LF- $\frac{1}{8}$ -EUV	
		G $\frac{1}{4}$	535656	MS4-LF- $\frac{1}{4}$ -CUV	535658	MS4-LF- $\frac{1}{4}$ -EUV	
MS6	manual rotary	G $\frac{1}{4}$	529627	MS6-LF- $\frac{1}{4}$ -CUM	529635	MS6-LF- $\frac{1}{4}$ -EUM	
		G $\frac{3}{8}$	529643	MS6-LF- $\frac{3}{8}$ -CUM	529651	MS6-LF- $\frac{3}{8}$ -EUM	
		G $\frac{1}{2}$	529611	MS6-LF- $\frac{1}{2}$ -CUM	529619	MS6-LF- $\frac{1}{2}$ -EUM	
	fully automatic	G $\frac{1}{4}$	529629	MS6-LF- $\frac{1}{4}$ -CUV	529637	MS6-LF- $\frac{1}{4}$ -EUV	
		G $\frac{3}{8}$	529645	MS6-LF- $\frac{3}{8}$ -CUV	529653	MS6-LF- $\frac{3}{8}$ -EUV	
		G $\frac{1}{2}$	529613	MS6-LF- $\frac{1}{2}$ -CUV	529621	MS6-LF- $\frac{1}{2}$ -EUV	

# Filters MS4/MS6-LF, MS series

Ordering data – Modular products

**M** Mandatory data →

Module No.	Series	Size	Function	Connection size	Grade of filtration	Bowl
527695 527668	MS	4, 6	LF	1/8, 1/4, 3/8, 1/2, AGA, AGB, AGC, AGD, AGE	E, C	R, U
<b>Order example</b>						
527695	MS	4	- LF	- AGB	- E	- R

**Ordering table**

Grid dimension	[mm]	40	62	Conditions	Code	Enter code
<b>M</b> Module No.		527695	527668			
Series		Standard			MS	MS
Size		4	6		...	
Function		Filters			-LF	-LF
Connection size		Thread G1/8	-		-1/8	
		Thread G1/4	Thread G1/4		-1/4	
		-	Thread G3/8		-3/8	
		-	Thread G1/2		-1/2	
		Connecting plate G1/8	-		-AGA	
		Connecting plate G1/4	Connecting plate G1/4		-AGB	
		Connecting plate G3/8	Connecting plate G3/8		-AGC	
		-	Connecting plate G1/2		-AGD	
Grade of filtration		40 µm			-E	
		5 µm			-C	
Bowl		Plastic bowl with plastic bowl guard			-R	
		Metal bowl			-U	

Transfer order code

	MS		-	LF		-		-	
--	----	--	---	----	--	---	--	---	--



# Filters MS4/MS6-LF, MS series

Ordering data – Modular products

→ M Mandatory data	O Options	
Condensate drain	Type of mounting	Alternative flow direction
M, H, V, E2, E3, E4	WP, WPM, WB, WBM	Z
- M	- WP	- Z

Ordering table						
Grid dimension	[mm]	40	62	Condition s	Code	Enter code
↓ M	Condensate drain	Manual			-M	
		Semi-automatic (P1 max. 12 bar)			-H	
		Fully automatic (P1 max. 12 bar)			-V	
		-	External fully automatic condensate drain, electrical, 110 V AC, terminals	1	-E2	
		-	External fully automatic condensate drain, electrical, 230 V AC, terminals	1	-E3	
-	External fully automatic condensate drain, electrical, 24 V DC, terminals	1	-E4			
O	Type of mounting	Mounting bracket		2	-WP	
		Mounting bracket		2	-WPM	
		Mounting bracket			-WB	
		Mounting bracket		-	-WBM	
	Alternative flow direction	Flow direction from right to left			-Z	

1 E2, E3, E4 Only with metal bowl U.

2 WP, WPM Only with connecting plate AGA, AGB, AGC, AGD or AGE.


Transfer order code

-  -  -


# Fine and micro filters MS4/MS6-LFM, MS series

Technical data


Function  
 Condensate drain  
 manual rotary  
 without differential pressure indicator




with differential pressure indicator or  
 filter pollution indicator



Condensate drain  
 semi or fully automatic  
 without differential pressure indicator



with differential pressure indicator or  
 filter pollution indicator



Flow rate  
 54 ... 3,000 l/min  
 Temperature range  
 -10 ... +60 °C  
 Pressure  
 0 ... 20 bar

www.festo.com/en/  
 Spare\_parts\_service  
 Wearing parts kits  
 → 27



- High-performance filter for exceptionally clean compressed air
- Air quality to ISO 8573-1:2010
- Available with manual, semi-automatic, fully automatic or fully automatic, electrically actuated condensate drain
- Available with differential pressure indicator for display of filter pollution
- Available with electronic filter pollution indicator
- Optionally with filter cartridge for low flow rates, suitable for sealing air and cleaning air
- Choice of filter cartridges: 0.01 µm or 1 µm
- New filter cartridges → 87

General technical data					
Size	MS4		MS6		
Pneumatic connection 1, 2	G1/8	G1/4	G1/4	G3/8	G1/2
Constructional design	Fibre filter				
Type of mounting	Via accessories In-line installation				
Mounting position	Vertical ±5°				
Grade of filtration [µm]	0.01 (micro filter MS-LFM-A) 1 (fine filter MS-LFM-B)				
Air purity class at the output	Compressed air in accordance with ISO 8573-1:2010 [1:7:2] (Grade of filtration 0.01µm, micro filter MS-LFM-A) Compressed air in accordance with ISO 8573-1:2010 [2:7:3] (Grade of filtration 1µm, fine filter MS-LFM-B)				
Filter efficiency [%]	99.9999 (Grade of filtration 0.01µm, micro filter MS-LFM-A) 99.99 (Grade of filtration 1µm, fine filter MS-LFM-B)				
Bowl guard	Plastic bowl guard Integrated as metal bowl				
Condensate drain	Manual rotary Semi-automatic Fully automatic – Fully automatic, electrically actuated				
Differential pressure indication <sup>1)</sup>	Visual display With filter pollution indicator based on differential pressure				
Residual oil content [mg/m <sup>3</sup> ]	≤0.01 (micro filter MS-LFM-A) ≤0.5 (fine filter MS-LFM-B)				
Max. condensate volume [cm <sup>3</sup> ]	19 (with plastic bowl guard) 25 (with metal shell)		38		

1) Recommended max. differential pressure for changing the filter cartridge is Δp<sub>1-2</sub> = 0.35 bar; for the micro filter MS6-LFM-A with range of application HP Δp<sub>1-2</sub> = 0.5 bar  
 Note: This product conforms to ISO 1179-1 and ISO 228-1

# Fine and micro filters MS4/MS6-LFM, MS series

Technical data

Standard flow rate $q_n^{1)}$ [l/min]				
Size	MS4	MS6		
Variant	Standard	Standard	High flow rate HF	Range of application HP, suitable for sealing air and cleaning air
Micro filter MS-LFM-A				
Max. standard flow rate for air purity class $q_{n \max}$	360	900	2,500	400
Min. standard flow rate for air purity class $q_{n \min}$	54	135	150	60
Fine filter MS-LFM-B				
Max. standard flow rate for air purity class $q_{n \max}$	360	950	3,000	500
Min. standard flow rate for air purity class $q_{n \min}$	54	140	188	60

1) Measured at  $p_1 = 6$  bar.

- | - 125 l/min must be available for the fully automatic condensate drain to close correctly.

Technical data – Filter pollution indicator				
Variant	DP	DN	DPI	DNI
Pressure measuring range [bar]	0 ... +1			
Measured variable	Differential pressure; percentage value for filter pollution			
Switch output	PNP	NPN	PNP	NPN
Analogue output [mA]	-		4 ... 20	
Operating voltage range [V DC]	15 ... 30			
Max. output current [mA]	150			
Protection class	IP65			
CE mark (see declaration of conformity)	In accordance with EU EMC directive			
	In accordance with EU Low Voltage Directive			

Operating and environmental conditions									
Variant	Condensate drain							Filter pollution indicator	
	Manual rotary		Semi-automatic		Fully automatic		Fully automatic, electrically actuated		
	M		H		V		E2/E3/E4	DP/DN/DPI/DNI	
Size	MS4	MS6	MS4	MS6	MS4	MS6	MS6	MS4	MS6
Operating pressure [bar]	0 ... 14	0 ... 20	1.5 ... 12	1.5 ... 12	2 ... 12	2 ... 12	0.8 ... 16	max. 10	
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [6:8:4] <sup>1)</sup>								
	Inert gases								
Ambient temperature [°C]	-10 ... +60		+5 ... +60		+5 ... +60		+1 ... +60	0 ... +50	
Temperature of medium [°C]	-10 ... +60		+5 ... +60		+5 ... +60		+1 ... +60	0 ... +50	
Storage temperature [°C]	-10 ... +60		-10 ... +60		-10 ... +60		+1 ... +60	0 ... +50	
Corrosion resistance class CRC <sup>2)</sup>	2								

1) It is recommended to prefilter the compressed air for the micro filter MS-LFM-A using a fine filter MS-LFM-B (grade of filtration 1 µm).

2) Corrosion resistance class 2 to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.


# Fine and micro filters MS4/MS6-LFM, MS series

Technical data

Weight [g]			
Size	MS4	MS6	
Variant	Standard	Standard/Range of application HP	High flow rate HF
Fine and micro filter with plastic bowl guard R	190	600	1,280
Fine and micro filter with metal bowl U	350	820	1,500
Fine and micro filter with metal bowl guard U and fully automatic, electrically actuated condensate drain E2/E3/E4	-	1,800	2,180
Filter pollution indicator	80	100	100

## Materials

Sectional view



Fine and micro filters	
1 Housing	Die-cast aluminium
2 Plastic bowl guard	PC
3 Metal bowl	Wrought aluminium alloy, die-cast aluminium
Viewing window	PA
4 Filter	Borosilicate fibre
- Seals	NBR
Note on materials	RoHS-compliant (not with variant E2, E3 or E4) Free of copper and PTFE



Filter pollution indicator	
Housing	PA POM
Adapter	PA
Display	PC
Seals	NBR
Note on materials	Free of copper and PTFE

## Standard flow rate $q_n$ as a function of the differential pressure $\Delta p_{1-2}$

Grade of filtration 0.01  $\mu\text{m}$

Grade of filtration 1  $\mu\text{m}$

MS4-LFM-1/8 and MS4-LFM-1/4



# Fine and micro filters MS4/MS6-LFM, MS series



Technical data

## Standard flow rate $q_n$ as a function of the differential pressure $\Delta p_{1-2}$



MS6-LFM-1/4

Grade of filtration 0.01  $\mu\text{m}$



Grade of filtration 1  $\mu\text{m}$



MS6-LFM-3/8



MS6-LFM-1/2




# Fine and micro filters MS4/MS6-LFM, MS series

Technical data




## Standard flow rate $q_n$ as a function of the differential pressure $p_{1-2}$


MS6-LFM-1/4-...-HF, Grade of filtration 0.01  $\mu\text{m}$




MS6-LFM-1/4-...-HF, Grade of filtration 1  $\mu\text{m}$




MS6-LFM-3/8-...-HF, Grade of filtration 0.01  $\mu\text{m}$




MS6-LFM-3/8-...-HF, Grade of filtration 1  $\mu\text{m}$



MS6-LFM-1/2-...-HF, Grade of filtration 0.01  $\mu\text{m}$



MS6-LFM-1/2-...-HF, Grade of filtration 1  $\mu\text{m}$



- p1: 4 bar ( $q_{\text{min}}$ : 103 l/min)
- - - p1: 6 bar ( $q_{\text{min}}$ : 125 l/min)
- - - p1: 8 bar
- - - p1: 10 bar ( $q_{\text{min}}$ : 162 l/min)
- - - p1: 14 bar ( $q_{\text{min}}$ : 192 l/min)
- - -  $q_{\text{max}}$

- p1: 4 bar ( $q_{\text{min}}$ : 124 l/min)
- - - p1: 6 bar ( $q_{\text{min}}$ : 150 l/min)
- - - p1: 8 bar
- - - p1: 10 bar ( $q_{\text{min}}$ : 194 l/min)
- - - p1: 14 bar ( $q_{\text{min}}$ : 230 l/min)
- - -  $q_{\text{max}}$

# Fine and micro filters MS4/MS6-LFM, MS series


Technical data

## Dimensions – Basic version

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Standard/Range of application HP,  
manual rotary condensate drain

High flow rate HF,  
manual rotary condensate drain




Type	B1	B2	B3	D1	L1		L2	L3	L5	L6	
					Bowl guard					Plastic	Metal
					Plastic	Metal					
MS4-LFM-1/8	40	21	54	G1/8	142	160	29	60	25	17.7	17.7
MS4-LFM-1/4				G1/4							
MS6-LFM-1/4	62	31	76	G1/4	193	199	42	87.5	75	16	19
MS6-LFM-3/8				G3/8							
MS6-LFM-1/2				G1/2							
MS6-LFM-1/4-...-HF	62	31	76	G1/4	313	319	42	207	75	16	19
MS6-LFM-3/8-...-HF				G3/8							
MS6-LFM-1/2-...-HF				G1/2							

Note: This product conforms to ISO 1179-1 and ISO 228-1

# Fine and micro filters MS4/MS6-LFM, MS series

Technical data

Dimensions – Differential pressure indicator DA Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)



Type	B1	B2	B3	D1	L1 Bowl guard		L2	L3
					Plastic	Metal		
MS4-LFM-1/8-...-DA	40	21	54	G1/8	168	186	55	86
MS4-LFM-1/4-...-DA				G1/4				
MS6-LFM-1/4-...-DA	62	31	76	G1/4	219	225	68	113
MS6-LFM-3/8-...-DA				G3/8				
MS6-LFM-1/2-...-DA				G1/2				
MS6-LFM-1/4-...-HF-DA	62	31	76	G1/4	339	345	68	113
MS6-LFM-3/8-...-HF-DA				G3/8				
MS6-LFM-1/2-...-HF-DA				G1/2				

Note: This product conforms to ISO 1179-1 and ISO 228-1




# Fine and micro filters MS4/MS6-LFM, MS series

Technical data



## Dimensions – Filter pollution indicator DP/DN/DPI/DNI

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)



Variant DP:  
Filter pollution indicator with 3-pin  
M8x1 plug, 1 switch output PNP

Variant DN:  
Filter pollution indicator with 3-pin  
M8x1 plug, 1 switch output NPN

Variant DPI:  
Filter pollution indicator with 4-pin  
M12x1 plug, 1 switch output PNP  
and 4 ... 20 mA analogue

Variant DNI:  
Filter pollution indicator with 4-pin  
M12x1 plug, 1 switch output NPN  
and 4 ... 20 mA analogue

Type	B2	B3	B4	D1	D6	L5	L6
MS4-LFM-1/8-...-DP/DN	21	81.8	32.3	G1/8	M8x1	32	47
MS4-LFM-1/4-...-DP/DN				G1/4			
MS4-LFM-1/8-...-DPI/DNI	21	81.8	32.3	G1/8	M12x1	32	56
MS4-LFM-1/4-...-DPI/DNI				G1/4			
MS6-LFM-1/4-...-DP/DN	31	102	32.3	G1/4	M8x1	32	47
MS6-LFM-3/8-...-DP/DN				G3/8			
MS6-LFM-1/2-...-DP/DN				G1/2			
MS6-LFM-1/4-...-DPI/DNI	31	102	32.3	G1/4	M12x1	32	56
MS6-LFM-3/8-...-DPI/DNI				G3/8			
MS6-LFM-1/2-...-DPI/DNI				G1/2			


Note: This product conforms to ISO 1179-1 and ISO 228-1

# Fine and micro filters MS4/MS6-LFM, MS series

Technical data


## Dimensions – Condensate drain Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

**Manual rotary M**




Barbed fitting for plastic tubing  
PCN-4

**Semi-automatic H**



QS fitting for plastic tubing  
PUN-6/PAN-6

**Fully automatic V**




Barbed fitting for plastic tubing  
PCN-4

Type	L6
<b>Plastic bowl guard</b>	
MS4-LFM-...-M	17.7
MS6-LFM-...-M	16
<b>Metal bowl</b>	
MS4-LFM-...-M	17.7
MS6-LFM-...-M	19

Type	L6
<b>Plastic bowl guard</b>	
MS4-LFM-...-H	22.1
MS6-LFM-...-H	20
<b>Metal bowl</b>	
MS4-LFM-...-H	22.1
MS6-LFM-...-H	23

Type	L6
<b>Plastic bowl guard</b>	
MS4-LFM-...-V	20.4
MS6-LFM-...-V	19
<b>Metal bowl</b>	
MS4-LFM-...-V	20.4
MS6-LFM-...-V	22

## Fully automatic, electrically actuated E2/E3/E4 Technical data → Internet: pwea



- Condensate drain PWEA:
- 2 Electrical connection: Screw terminal PG9
  - 3 Connection 360° rotatable for plastic tubing PUN-H-12x2

# Fine and micro filters MS4/MS6-LFM, MS series

FESTO

Technical data

Ordering data						
Without differential pressure indicator						
Size	Condensate drain	Connection	Micro filter		Fine filter	
			Grade of filtration 0.01 µm		Grade of filtration 1 µm	
			Part No.	Type	Part No.	Type
Plastic bowl guard						
MS4	Manual rotary	G $\frac{1}{8}$	529463	MS4-LFM- $\frac{1}{8}$ -ARM	529465	MS4-LFM- $\frac{1}{8}$ -BRM
		G $\frac{1}{4}$	529459	MS4-LFM- $\frac{1}{4}$ -ARM	529461	MS4-LFM- $\frac{1}{4}$ -BRM
MS6	Manual rotary	G $\frac{1}{4}$	529663	MS6-LFM- $\frac{1}{4}$ -ARM	529667	MS6-LFM- $\frac{1}{4}$ -BRM
		G $\frac{3}{8}$	529671	MS6-LFM- $\frac{3}{8}$ -ARM	529675	MS6-LFM- $\frac{3}{8}$ -BRM
		G $\frac{1}{2}$	529655	MS6-LFM- $\frac{1}{2}$ -ARM	529659	MS6-LFM- $\frac{1}{2}$ -BRM
	Fully automatic	G $\frac{1}{4}$	530510	MS6-LFM- $\frac{1}{4}$ -ARV	530514	MS6-LFM- $\frac{1}{4}$ -BRV
		G $\frac{3}{8}$	530518	MS6-LFM- $\frac{3}{8}$ -ARV	530522	MS6-LFM- $\frac{3}{8}$ -BRV
		G $\frac{1}{2}$	530502	MS6-LFM- $\frac{1}{2}$ -ARV	530506	MS6-LFM- $\frac{1}{2}$ -BRV
Integrated as metal bowl						
MS4	Fully automatic	G $\frac{1}{8}$	539208	MS4-LFM- $\frac{1}{8}$ -AUV	539204	MS4-LFM- $\frac{1}{8}$ -BUV
		G $\frac{1}{4}$	535768	MS4-LFM- $\frac{1}{4}$ -AUV	535766	MS4-LFM- $\frac{1}{4}$ -BUV
MS6	Fully automatic	G $\frac{1}{4}$	529665	MS6-LFM- $\frac{1}{4}$ -AUV	529669	MS6-LFM- $\frac{1}{4}$ -BUV
		G $\frac{3}{8}$	529673	MS6-LFM- $\frac{3}{8}$ -AUV	529677	MS6-LFM- $\frac{3}{8}$ -BUV
		G $\frac{1}{2}$	529657	MS6-LFM- $\frac{1}{2}$ -AUV	529661	MS6-LFM- $\frac{1}{2}$ -BUV

Ordering data						
With differential pressure indicator						
Size	Condensate drain	Connection	Micro filter		Fine filter	
			Grade of filtration 0.01 µm		Grade of filtration 1 µm	
			Part No.	Type	Part No.	Type
Plastic bowl guard						
MS4	Manual rotary	G $\frac{1}{8}$	536821	MS4-LFM- $\frac{1}{8}$ -ARM-DA	536817	MS4-LFM- $\frac{1}{8}$ -BRM-DA
		G $\frac{1}{4}$	536822	MS4-LFM- $\frac{1}{4}$ -ARM-DA	536818	MS4-LFM- $\frac{1}{4}$ -BRM-DA
MS6	Manual rotary	G $\frac{1}{4}$	536869	MS6-LFM- $\frac{1}{4}$ -ARM-DA	536833	MS6-LFM- $\frac{1}{4}$ -BRM-DA
		G $\frac{3}{8}$	536870	MS6-LFM- $\frac{3}{8}$ -ARM-DA	536834	MS6-LFM- $\frac{3}{8}$ -BRM-DA
		G $\frac{1}{2}$	536871	MS6-LFM- $\frac{1}{2}$ -ARM-DA	536835	MS6-LFM- $\frac{1}{2}$ -BRM-DA
	Fully automatic	G $\frac{1}{4}$	536875	MS6-LFM- $\frac{1}{4}$ -ARV-DA	536839	MS6-LFM- $\frac{1}{4}$ -BRV-DA
		G $\frac{3}{8}$	536876	MS6-LFM- $\frac{3}{8}$ -ARV-DA	536840	MS6-LFM- $\frac{3}{8}$ -BRV-DA
		G $\frac{1}{2}$	536877	MS6-LFM- $\frac{1}{2}$ -ARV-DA	536841	MS6-LFM- $\frac{1}{2}$ -BRV-DA
Integrated as metal bowl						
MS4	Fully automatic	G $\frac{1}{8}$	537213	MS4-LFM- $\frac{1}{8}$ -AUV-DA	537209	MS4-LFM- $\frac{1}{8}$ -BUV-DA
		G $\frac{1}{4}$	537214	MS4-LFM- $\frac{1}{4}$ -AUV-DA	537210	MS4-LFM- $\frac{1}{4}$ -BUV-DA
MS6	Fully automatic	G $\frac{1}{4}$	536881	MS6-LFM- $\frac{1}{4}$ -AUV-DA	536845	MS6-LFM- $\frac{1}{4}$ -BUV-DA
		G $\frac{3}{8}$	536882	MS6-LFM- $\frac{3}{8}$ -AUV-DA	536846	MS6-LFM- $\frac{3}{8}$ -BUV-DA
		G $\frac{1}{2}$	536883	MS6-LFM- $\frac{1}{2}$ -AUV-DA	536847	MS6-LFM- $\frac{1}{2}$ -BUV-DA
Integrated as metal bowl and high flow rate						
MS6	Fully automatic	G $\frac{1}{2}$	552926	MS6-LFM- $\frac{1}{2}$ -AUV-HF-DA	552925	MS6-LFM- $\frac{1}{2}$ -BUV-HF-DA

Ordering data – Wearing parts kits		
Size	Part No.	Type
MS4	673641	MS4-LFM
MS6	673642	MS6-LFM

# Fine and micro filters MS4/MS6-LFM, MS series



Ordering data – Modular products

**M** Mandatory data →

Module No.	Series	Size	Function	Connection size	Grade of filtration	Bowl
527697 527670	MS	4, 6	LFM	1/8, 1/4, 3/8, 1/2, AGA, AGB, AGC, AGD, AGE	B, A	R, U
<b>Ordering example</b>						
<b>527697</b>	<b>MS</b>	<b>4</b>	<b>- LFM</b>	<b>- AGB</b>	<b>- B</b>	<b>- R</b>

**Ordering table**

Grid dimension	[mm]	40	62	Conditions	Code	Enter code
<b>M</b> Module No.		<b>527697</b>	<b>527670</b>			
Series		Standard			<b>MS</b>	MS
Size		4	6		...	
Function		Fine and micro filter			<b>-LFM</b>	-LFM
Connection size		Thread G1/8	-		-1/8	
		Thread G1/4	Thread G1/4		-1/4	
		-	Thread G3/8		-3/8	
		-	Thread G1/2		-1/2	
		Connecting plate G1/8	-		<b>-AGA</b>	
		Connecting plate G1/4	Connecting plate G1/4		<b>-AGB</b>	
		Connecting plate G3/8	Connecting plate G3/8		<b>-AGC</b>	
		-	Connecting plate G1/2		<b>-AGD</b>	
Grade of filtration		1 µm			<b>-B</b>	
		0.01 µm			<b>-A</b>	
Bowl		Plastic bowl with plastic bowl guard			<b>-R</b>	
		Metal bowl			<b>-U</b>	

Transfer order code

	<b>MS</b>		<b>- LFM</b>				
--	-----------	--	--------------	--	--	--	--

# Fine and micro filters MS4/MS6-LFM, MS series

Ordering data – Modular products

→ M Mandatory data		O Options			
Condensate drain	Flow rate	Range of application	Filter contamination sensing	Type of mounting	Alternative flow direction
M, H, V, E2, E3, E4	HF	HP	DA, DP, DN, DPI, DNI	WP, WPM, WB, WBM	Z
- M	-	-	-	- WP	- Z

Ordering table						
Grid dimension	[mm]	40	62	Condition s	Code	Enter code
↓ Condensate drain M	Manual				-M	
	Semi-automatic (P1 max. 12 bar)				-H	
	Fully automatic (P1 max. 12 bar)			1	-V	
	-	External fully automatic condensate drain, electrical, 110 V AC, terminals		2	-E2	
	-	External fully automatic condensate drain, electrical, 230 V AC, terminals		2	-E3	
	-	External fully automatic condensate drain, electrical, 24 V DC, terminals		2	-E4	
O	Flow rate	-	High flow rate		-HF	
	Range of application	-	Suitable for sealing air and cleaning air	3	-HP	
	Filter contamination sensing	Differential pressure indicator, visual			-DA	
		Filter contamination indicator, M8 plug, PNP, 3-pin		4	-DP	
		Filter contamination indicator, M8 plug, NPN, 3-pin		4	-DN	
		Filter contamination indicator, M12 plug, PNP, 4-pin, analogue output 4 ... 20 mA		4	-DPI	
		Filter contamination indicator, M12 plug, PNP, 4-pin, analogue output 4 ... 20 mA		4	-DNI	
	Type of mounting	Mounting bracket		5	-WP	
		Mounting bracket		5	-WPM	
		Mounting bracket			-WB	
		Mounting bracket		-	-WBM	
	Alternative flow direction	Flow direction from right to left			-Z	

1 V Size 4: only with metal bowl U

2 E2, E3, E4 Only with metal bowl U

3 HP Not with flow rate HF or filter contamination sensing DA

4 DP, DN, DPI, DNI

Measuring range max. 10 bar

5 WP, WPM Only with connecting plate AGA, AGB, AGC, AGD or AGE


Transfer order code

- [ ] - [ ] - [ ] - [ ] - [ ] - [ ]

# Active carbon filters MS4/MS6-LFX, MS series

## Technical data

### Function



Flow rate  
max. 2,500 l/min  
Temperature range  
-10 ... +60 °C  
Pressure  
0 ... 20 bar



### Note

Prefiltration with micro filter  
MS-LFM-A, grade of filtration  
0.01 µm, recommended.

- Removal of liquid and gaseous oil particles from compressed air using active carbon
- Eliminates odours and vapours
- Optionally with filter cartridge for low flow rates, suitable for sealing air and cleaning air
- New filter cartridges → 87

General technical data					
Size	MS4		MS6		
Pneumatic connection 1, 2	G <sup>1</sup> / <sub>8</sub>	G <sup>1</sup> / <sub>4</sub>	G <sup>1</sup> / <sub>4</sub>	G <sup>3</sup> / <sub>8</sub>	G <sup>1</sup> / <sub>2</sub>
Design	Active carbon filter				
Type of mounting	Via accessories				
	In-line installation				
Assembly position	Vertical ±5°				
Air purity class at the output <sup>1)</sup>	Compressed air in accordance with ISO 8573-1:2010 [1:4:1]				
Bowl guard	Plastic bowl guard				
	Integrated as metal bowl				
Residual oil content [mg/m <sup>3</sup> ]	≤0.003				

1) We recommend that the filter cartridge be replaced by a new one after 1,000 operating hours. (Applies to an ambient temperature of 21 °C. At higher temperatures the service life of the filter cartridge will be reduced.)

Note: This product conforms to ISO 1179-1 and ISO 228-1

Standard flow rate q <sub>n</sub> <sup>1)</sup> [l/min]				
Size	MS4		MS6	
Variant	Standard		High flow rate HF	Range of application HP, suitable for sealing air and cleaning air
Max. standard flow rate for air purity class q <sub>n</sub> max	360		900	2,500

1) Measured at p<sub>1</sub> = 6 bar.

# Active carbon filters MS4/MS6-LFX, MS series

Technical data


Operating and environmental conditions		
Size	MS4	MS6
Operating pressure [bar]	0 ... 14	0 ... 20
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [1:4:2] Inert gases	
Ambient temperature [°C]	-10 ... +60	
Temperature of medium [°C]	+5 ... +30	
Storage temperature [°C]	-10 ... +60	
Corrosion resistance CRC <sup>1)</sup>	2	

1) Corrosion resistance class 2 according to Festo standard 940 070  
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Weights [g]			
Size	MS4	MS6	
Variant	Standard	Standard/Range of application HP	High flow rate HF
Active carbon filter with plastic bowl guard R	190	600	1,280
Active carbon filter with metal bowl U	350	820	1,500

## Materials

Sectional view




Active carbon filter	
1 Body	Die-cast aluminium
2 Plastic bowl guard	PC
3 Metal bowl	Wrought aluminium alloy, die-cast aluminium
Viewing window	PA
4 Filters	Active carbon
- Seals	NBR
Note on materials	RoHS-compliant
	Free of copper and PTFE

# Active carbon filters MS4/MS6-LFX, MS series


Technical data

## Standard flow rate $q_n$ as a function of the differential pressure $\Delta p_{1-2}$


MS4-LFX-1/8 and MS4-LFX-1/4




MS6-LFX-1/4



MS6-LFX-3/8



MS6-LFX-1/2






# Active carbon filters MS4/MS6-LFX, MS series


Technical data

## Standard flow rate $q_n$ as a function of the differential pressure $p_{1-2}$


MS6-LFX-1/4-...-HF



MS6-LFX-3/8-...-HF



MS6-LFX-1/2-...-HF




- p1: 4 bar
- - - p1: 6 bar
- · - p1: 8 bar
- · · - p1: 10 bar
- · · · p1: 14 bar
- - - -  $q_{max}$

# Active carbon filters MS4/MS6-LFX, MS series



Technical data



Type	B1	B2	B3	D1	L1 Bowl guard		L2	L3	L5
					Plastic	Metal			
MS4-LFX-1/8	40	21	54	G1/8	142.8	160.4	29	60	73
MS4-LFX-1/4				G1/4					
MS6-LFX-1/4	62	31	76	G1/4	192	198	42	87	100
MS6-LFX-3/8				G3/8					
MS6-LFX-1/2				G1/2					
MS6-LFX-1/4-...-HF	62	31	76	G1/4	312	318	42	207	100
MS6-LFX-3/8-...-HF				G3/8					
MS6-LFX-1/2-...-HF				G1/2					

Note: This product conforms to ISO 1179-1 and ISO 228-1

Ordering data					
Size	Connection	Plastic bowl guard		Integrated as metal bowl	
		Part No.	Type	Part No.	Type
MS4	G1/8	536707	MS4-LFX-1/8-R	536709	MS4-LFX-1/8-U
	G1/4	529467	MS4-LFX-1/4-R	535782	MS4-LFX-1/4-U
MS6	G1/4	529683	MS6-LFX-1/4-R	529685	MS6-LFX-1/4-U
	G3/8	529687	MS6-LFX-3/8-R	529689	MS6-LFX-3/8-U
	G1/2	529679	MS6-LFX-1/2-R	529681	MS6-LFX-1/2-U
<b>High flow rate</b>					
MS6	G1/2	-	-	552927	MS6-LFX-1/2-U-HF

# Activated carbon filters MS4/MS6-LFX, MS series

Ordering data – Modular products

M Mandatory data					O Options				
Module No.	Series	Size	Function	Connection size	Bowl	Flow rate	Range of application	Type of mounting	Alternative flow direction
527699 527672	MS	4 6	LFX	1/8, 1/4, 3/8, 1/2, AGA, AGB, AGC, AGD, AGE	R U	HF	HP	WP WPM WB WBM	Z
<b>Ordering example</b>									
527699	MS	4	LFX	AGB	R			WP	Z

Ordering table						
Grid dimension	[mm]	40	62	Condition s	Code	Enter code
M	Module No.	527699	527672			
	Series	Standard			MS	MS
	Size	4	6		...	
	Function	Activated carbon filter			-LFX	-LFX
	Connection size	Thread G1/8	-	-1/8		
		Thread G1/4	Thread G1/4	-1/4		
		-	Thread G3/8	-3/8		
		-	Thread G1/2	-1/2		
		Connecting plate G1/8	-	-AGA		
		Connecting plate G1/4	Connecting plate G1/4	-AGB		
		Connecting plate G3/8	Connecting plate G3/8	-AGC		
		-	Connecting plate G1/2	-AGD		
		Connecting plate G3/4	-AGE			
	Bowl	Plastic bowl with plastic bowl guard			-R	
		Metal bowl			-U	
	Flow rate	-	High flow rate	-HF		
	Range of application	-	Suitable for sealing air and cleaning air	1	-HP	
	Type of mounting	Mounting bracket			2	-WP
		Mounting bracket			2	-WPM
		Mounting bracket				-WB
		Mounting bracket				-WBM
	Alternative flow direction	Flow direction from right to left			-Z	


- 1 HP Not with flow rate HF
- 2 WP, WPM Only with connecting plate AGA, AGB, AGC, AGD or AGE

Transfer order code

	MS		-	LFX	-		-		-		-		-		-	
--	----	--	---	-----	---	--	---	--	---	--	---	--	---	--	---	--

**Filters MS9-LF, MS series**

Peripherals overview



**Note**  
Additional accessories:  
– Module connector for combination with size MS6, MS9 or MS12 → Internet: rmv, armv

Mounting attachments and accessories					
	Individual device	With connecting plate AG...		Combination Module without connecting thread, without connecting plate G	→ Page/ Internet
		With female thread ¾ or 1	Without EU certification EX4		
		1	Connecting plate MS9-AG...	–	
2	Module connector MS9-MV	–	–	■	ms9-mv
3	Mounting bracket MS9-WP	■	■	■	ms9-wp
4	Mounting bracket MS9-WPB	■	■	■	ms9-wp
5	Mounting bracket MS9-WPM	■	■	–	ms9-wp
6	Condensate drain, fully automatic, electrically actuated E2/E3/E4	■	■	■	42

## Filters MS9-LF, MS series

Type codes

**FESTO**

		MS	9	-	LF	-	G	-	E	U	M	
<b>Series</b>												
MS	Standard service unit											
<b>Size</b>												
9	Grid dimension 90 mm											
<b>Service function</b>												
LF	Filter											
<b>Connection size</b>												
G	Module without connecting thread, without connecting plate											
<b>Grade of filtration</b>												
C	5 µm											
E	40 µm											
<b>Bowl guard</b>												
U	Integrated as metal bowl											
<b>Condensate drain</b>												
M	Manual rotary											
V	Fully automatic											

Additional variants can be ordered using the modular system → 42

- Connecting plates
- Condensate drain
- Type of mounting
- EU certification
- UL certification
- Alternative flow direction


**New**  
**Variant EX4, UL1**

**Filters MS9-LF, MS series**


Technical data



Condensate drain,  
manual rotary



Condensate drain,  
semi or fully automatic



Flow rate  
6,000 ... 16,000 l/min  
Temperature range  
-10 ... +60 °C  
Pressure  
0 ... 20 bar



- Good particle and condensate separation
- High flow rate with minimal pressure drop
- Available with manual, semi-automatic, fully automatic or fully automatic, electrically actuated condensate drain
- Choice of filter cartridges: 5 µm or 40 µm
- New filter cartridges → 88
- Optional device variant EX4 for use in potentially explosive areas in zones 1, 2, 21 and 22

General technical data				
Size	MS9			
Pneumatic connection 1, 2	G3/4	G1	G1/2 ... G1 1/2 (with connecting plate AG...)	- (without connecting thread G)
Design	Sintered filter with centrifugal separator			
Type of mounting	Via accessories In-line installation			
Mounting position	Vertical ±5°			
Grade of filtration [µm]	5 40			
Air purity class at the output	Compressed air in accordance with ISO 8573-1:2010 [6:8:4] (grade of filtration 5 µm) Compressed air in accordance with ISO 8573-1:2010 [7:8:4] (grade of filtration 40 µm)			
Bowl guard	Integrated as metal bowl			
Condensate drain	Manual rotary Semi-automatic Fully automatic Fully automatic, electrically actuated			
Max. condensate volume [ml]	220			

Note: This product conforms to ISO 1179-1 and ISO 228-1

Standard nominal flow rate q <sub>nN</sub> <sup>1)</sup> [l/min]				
Pneumatic connection	Connecting plate AGD	Thread G3/4 or connecting plate AGE	Thread G1 or connecting plate AGF/AGG/AGH	
Grade of filtration	5 µm	6,000	8,500	9,500
	40 µm	8,000	12,500	16,000

1) Measured at p<sub>1</sub> = 6 bar and Δp = 1 bar

## Filters MS9-LF, MS series

Technical data

**FESTO**

Operating and environmental conditions				
Condensate drain	Manual rotary	Semi-automatic	Fully automatic	Fully automatic, electrically actuated
	M	H	V	E2/E3/E4
Operating pressure [bar]	0 ... 20	1.5 ... 12	2 ... 12	1 ... 16
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [--:9:-]	Compressed air in accordance with ISO 8573-1:2010 [--:9:-]	Compressed air in accordance with ISO 8573-1:2010 [7:9:-]	Compressed air in accordance with ISO 8573-1:2010 [--:9:-]
Ambient temperature [°C]	-10 ... +60	+5 ... +60	+5 ... +60	+1 ... +60
Temperature of medium [°C]	-10 ... +60	+5 ... +60	+5 ... +60	+1 ... +60
Storage temperature [°C]	-10 ... +60	+5 ... +60	+5 ... +60	+1 ... +60
Corrosion resistance class CRC <sup>1)</sup>	2			
Certification (variant UL1)	cULus recognized (OL)			


1) Corrosion resistance class 2 according to Festo standard 940 070  
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

ATEX	
EU certification	EX4
ATEX category gas	II 2G
Ex-ignition protection type gas	c T6 X
ATEX category dust	II 2D
EX-ignition protection type dust	c 60 °C X
ATEX ambient temperature	+5 °C ≤ Ta ≤ +60 °C
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)

Weight [g]	
Filter	2,000
Filter with condensate drain, fully automatic, electrically actuated E2/E3/E4	2,400

### Materials

Sectional view



Filter		
1	Housing	Die-cast aluminium
2	Bowl	Wrought aluminium alloy
	Inspection window	PA
3	Filter	PE
4	Spin disc	POM
5	Filter holder	POM
6	Separating plate	POM
-	Cover	PA reinforced
-	Connecting plate, module connector, mounting bracket	Die-cast aluminium
-	Seals	NBR
Note on materials		RoHS-compliant (not with variant E2, E3 or E4)

**New**  
**Variant EX4, UL1**

**Filters MS9-LF, MS series**


Technical data

**FESTO**

**Standard flow rate  $q_n$  as a function of differential pressure  $\Delta p_{1-2}$**


Grade of filtration 5  $\mu\text{m}$

MS9-LF-1/AGF, pneumatic connection G1



Grade of filtration 40  $\mu\text{m}$

MS9-LF-1/AGF, pneumatic connection G1




— 4 bar                      - · - 10 bar  
- - - 6 bar                     · · · 12 bar

**Dimensions – Basic version**

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Without connecting thread G



1 Installation dimensions

→ Flow direction

Type	B1	B2	B3	L1	L2	L4	L5	L6
MS9-LF-G	90	45	109	310.5	62	120	150	34.5



## Filters MS9-LF, MS series

Technical data


**FESTO**

### Dimensions – Connecting thread/connecting plate

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

With connecting thread 3/4 or 1

With connecting plate AG...



2 Mounting screw M6xmin.90 to DIN 912 (not included in the scope of delivery) for wall mounting without mounting bracket

3 Earthing screw M4x8 (only with MS9-...-EX4)

→ Flow direction


Type	B4	B5	B6	B7		B8	D1	D4	D5	L7	L8		T1	☞
					EX4							EX4		
MS9-LF-3/4	90	104	91.5	-	-	-	G3/4	11	6.5	66	-	6	-	
MS9-LF-1						-	G1							
MS9-LF-AGD	-	-	-	112	122	132	G1/2	-	-	-	35	-	30	
MS9-LF-AGE						132	G3/4						36	
MS9-LF-AGF						142	G1						41	
MS9-LF-AGG						162	G1 1/4						50	
MS9-LF-AGH						176	G1 1/2						55	

Note: This product conforms to ISO 1179-1 and ISO 228-1

### Dimensions – Condensate drain


Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Manual rotary M/fully automatic V



Barbed fitting for plastic tubing  
PCN-4


Semi-automatic H



QS connector for plastic tubing  
PUN-6/PAN-6

Fully automatic, electrically actuated E2/E3/E4

Technical data → Internet: pwea



Condensate drain PWEA:

- 2 Electrical connection: Screw terminal PG9
- 3 Connection 360° rotatable for plastic tubing PUN-H-12x2

Type	B1	D1	H1	L1	L2	L3
MS9-LF-...-M/V	-	5	34.5	-	-	-
MS9-LF-...-H		6				
MS9-LF-...-E2/E3/E4	72	-	178	140	108	15

### Ordering data

Size	Condensate drain	Connection	Grade of filtration 5 µm		Grade of filtration 40 µm	
			Part No.	Type	Part No.	Type
MS9	Manual rotary	-	564108	MS9-LF-G-CUM	564106	MS9-LF-G-EUM
	Fully automatic	-	564109	MS9-LF-G-CUV	564107	MS9-LF-G-EUV

**New**  
**Variant EX4, UL1**

**Filters MS9-LF, MS series**

Ordering data – Modular products



**M** Mandatory data →

Module No.	Series	Size	Function	Connection size	Grade of filtration	Bowl
562532	MS	9	LF	¾, 1, AGD, AGE, AGF, AGG, AGH, G	E, C	U
<b>Ordering example</b>						
562532	MS	9	- LF	- AGD	- E	- U

**Ordering table**

Grid dimension	[mm]	90	Conditions	Code	Enter code
<b>M</b> Module No.	562532				
Series	Standard			MS	MS
Size	9			9	9
Function	Filter			-LF	-LF
Connection size	Thread G¾		1	-¾	
	Thread G1		1	-1	
	Connecting plate G½			-AGD	
	Connecting plate G¾			-AGE	
	Connecting plate G1			-AGF	
	Connecting plate G1¼			-AGG	
	Connecting plate G1½			-AGH	
	Module without connecting thread, without connecting plate		1	-G	
Grade of filtration	40 µm			-E	
	5 µm			-C	
Bowl	Metal bowl			-U	-U

1 ¾, 1, G, E2, E3, E4, WPM

Not with EU certification EX4

Transfer order code

562532	MS	9	- LF	-		-		- U
--------	----	---	------	---	--	---	--	-----

## Filters MS9-LF, MS series

Ordering data – Modular products

→ <b>M</b> Mandatory data		<b>O</b> Options		
<b>Condensate drain</b>	<b>Type of mounting</b>	<b>EU certification</b>	<b>UL certification</b>	<b>Alternative flow direction</b>
M, H, V, E2, E3, E4	WP, WPM, WPB	EX4	UL1	Z
- <b>M</b>	- <b>WP</b>	-	-	- <b>Z</b>

Ordering table					
Grid dimension	[mm]	90	Condition s	Code	Enter code
↓ <b>M</b>	Condensate drain	Manual		-M	
		Semi-automatic (P1 max. 12 bar)		-H	
		Fully automatic (P1 max. 12 bar)		-V	
	External, fully automatic, electric	110 V AC, terminals (P1 max. 16 bar)	1	-E2	
		230 V AC, terminals (P1 max. 16 bar)	1	-E3	
		24 V DC, terminals (P1 max. 16 bar)	1	-E4	
<b>O</b>	Type of mounting	Mounting bracket	2	-WP	
		Mounting bracket	1 2	-WPM	
		Mounting bracket for large wall gap	2	-WPB	
	EU certification	II 2GD to EU Directive 94/9/EG		-EX4	
	UL certification	cULus, ordinary location for Canada and USA		-UL1	
	Alternative flow direction	Flow direction from right to left		-Z	

1 ¾, 1, G, E2, E3, E4, WPM

Not with EU certification EX4

2 WP, WPM, WPB


Not with module G

Transfer order code

-  -  -  -  -

## Fine and micro filters MS9-LFM, MS series

Peripherals overview



**Note**

Other accessories:

- Module connector for combination with size MS6, MS9 or MS12

→ Internet: rmv, armv

Mounting attachments and accessories					
	Individual device	With connecting plate AG...		Combination Module without connecting thread, without connecting plate G	→ Page/ Internet
		With female thread ¾ or 1	Without EU certification EX4		
1	Connecting plate MS9-AG...	–	■	■	ms9-ag
2	Module connector MS9-MV	–	–	■	ms9-mv
3	Mounting bracket MS9-WP	■	■	■	ms9-wp
4	Mounting bracket MS9-WPB	■	■	■	ms9-wp
5	Mounting bracket MS9-WPM	■	■	–	ms9-wp
6	Condensate drain, fully automatic, electrically actuated E2/E3/E4	■	■	■	56

## Fine and micro filters MS9-LFM, MS series

**FESTO**

Type codes

		MS	9	-	LFM	-	1	-	A	U	M	-	HF	-	DA
<b>Series</b>															
MS	Standard service unit														
<b>Size</b>															
9	Grid dimension 90 mm														
<b>Service function</b>															
LFM	Fine and micro filter														
<b>Pneumatic connection</b>															
3/4	Thread G3/4														
1	Thread G1														
G	Module without connecting thread, without connecting plate														
<b>Grade of filtration</b>															
A	0.01 µm														
B	1 µm														
<b>Bowl guard</b>															
U	Integrated as metal bowl														
<b>Condensate drain</b>															
M	Manual rotary														
V	Fully automatic														
<b>Flow rate</b>															
	Standard														
HF	High flow rate														
<b>Filter contamination sensor</b>															
	Without differential pressure indicator														
DA	Differential pressure indicator														

Further variants can be ordered using the modular system → 56

- Connecting plates
- Condensate drain
- Type of mounting
- EU certification
- UL certification
- Alternative flow direction

## Fine and micro filters MS9-LFM, MS series


**FESTO**

Technical data


Condensate drain

Manual rotary

Without differential pressure indicator




With differential pressure indicator




Condensate drain

Semi or fully automatic

Without differential pressure indicator



With differential pressure indicator



Flow rate

325 ... 10,000 l/min

Temperature range

-10 ... +60 °C

Pressure

0 ... 20 bar



- High-performance filter for exceptionally clean compressed air
- Air quality to ISO 8573-1:2010
- Available with manual, semi-automatic, fully automatic or fully automatic, electrically actuated condensate drain
- Available with differential pressure indicator for indication of contamination
- Choice of filter cartridges: 0.01 µm or 1 µm
- New filter cartridges → 88
- Optional device variant EX4 for use in potentially explosive areas in zones 1, 2, 21 and 22

General technical data				
Size	MS9			
Pneumatic connection 1, 2	G3/4	G1	G1/2 ... G1 1/2 (with connecting plate AG...)	– (without connecting thread G)
Constructional design	Fibre filter			
Type of mounting	Via accessories In-line installation			
Installation position	Vertical ±5°			
Grade of filtration [µm]	0.01 (micro filter MS9-LFM-A) 1 (fine filter MS9-LFM-B)			
Air purity class at the output	Compressed air in accordance with ISO 8573-1:2010 [1:7:2] (micro filter MS9-LFM-A) Compressed air in accordance with ISO 8573-1:2010 [2:7:3] (fine filter MS9-LFM-B)			
Filter efficiency [%]	99.9999 (Grade of filtration 0.01 µm, micro filter MS9-LFM-A) 99.99 (Grade of filtration 1 µm, fine filter MS9-LFM-B)			
Bowl guard	Integrated as metal bowl			
Condensate drain	Manual rotary Semi-automatic Fully automatic Fully automatic, electrically actuated			
Differential pressure indicator	Visual indicator			
Residual oil content [mg/m³]	≤0.01 (micro filter MS9-LFM-A) ≤0.5 (fine filter MS9-LFM-B)			
Max. condensate volume [cm³]	225			

Note: This product conforms to ISO 1179-1 and ISO 228-1

## Fine and micro filters MS9-LFM, MS series

**FESTO**

Technical data

Standard flow rate $q_n^{1)}$ [l/min]		
Version	Standard	High flow rate HF
<b>Micro filter MS9-LFM-A</b>		
Max. standard flow rate for air purity class $q_{n \max}$	6,500	7,800
Min. standard flow rate for air purity class $q_{n \min}$	325	390
<b>Fine filter MS9-LFM-B</b>		
Max. standard flow rate for air purity class $q_{n \max}$	7,000	10,000
Min. standard flow rate for air purity class $q_{n \min}$	350	500

1) Measured at  $p_1 = 6 \text{ bar}$

Operating and environmental conditions				
Condensate drain	Manual rotary	Semi-automatic	Fully automatic	Fully automatic, electrically actuated
	M	H	V	E2/E3/E4
Operating pressure [bar]	0 ... 20	1.5 ... 12	2 ... 12	0.8 ... 16
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [6:8:4] <sup>1)</sup>			
Ambient temperature [°C]	-10 ... +60	+5 ... +60	+5 ... +60	+1 ... +60
Temperature of medium [°C]	-10 ... +60	+5 ... +60	+5 ... +60	+1 ... +60
Storage temperature [°C]	-10 ... +60	+5 ... +60	-10 ... +60	+1 ... +60
Corrosion resistance class CRC <sup>2)</sup>	2			
Certification (variant UL1)	cULus recognized (OL)			

1) It is recommended to prefilter the compressed air for the micro filter MS-LFM-A using a fine filter MS-LFM-B (grade of filtration 1  $\mu\text{m}$ ).

2) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

ATEX	
EU certification	EX4
ATEX category gas	II 2G
Ex-ignition protection type gas	c T6 X
ATEX category dust	II 2D
EX-ignition protection type dust	c 60 °C X
ATEX ambient temperature	+5 °C $\leq$ $T_a \leq$ +60 °C
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)

**New**  
**Variant EX4, UL1**

**Fine and micro filters MS9-LFM, MS series**


**FESTO**

Technical data

Weights [g]		
Version	Standard	High flow rate HF
Fine and micro filter	2,000	2,500
Fine and micro filter with condensate drain fully automatic, electrically actuated E2/E3/E4	2,900	2,900

**Materials**

Sectional view



Fine and micro filters		
1	Housing	Die-cast aluminium
2	Bowl	Wrought aluminium alloy
	Inspection window	PA
3	Filter	Borosilicate fibre
-	Cover	PA reinforced
-	Connecting plate, module connector, mounting bracket	Die-cast aluminium
-	Seals	NBR
Note on materials		Free of copper and PTFE




## Fine and micro filters MS9-LFM, MS series

Technical data

### Standard flow rate $q_n$ as a function of the differential pressure $p_{1-2}$


Grade of filtration  $0.01 \mu\text{m}$

MS9-LFM-AGD, Pneumatic connection  $G\frac{1}{2}$




Grade of filtration  $0.01 \mu\text{m}$

MS9-LFM- $\frac{3}{4}$ /AGE, Pneumatic connection  $G\frac{3}{4}$




Grade of filtration  $0.01 \mu\text{m}$

MS9-LFM-1/AGE, Pneumatic connection  $G1$





Grade of filtration  $0.01 \mu\text{m}$

MS9-LFM-AGG, Pneumatic connection  $G1\frac{1}{4}$



Grade of filtration  $0.01 \mu\text{m}$

MS9-LFM-AGH, Pneumatic connection  $G1\frac{1}{2}$




## Fine and micro filters MS9-LFM, MS series

Technical data

### Standard flow rate $q_n$ as a function of the differential pressure $p_{1-2}$


Grade of filtration  $1\ \mu\text{m}$

MS9-LFM-AGD, Pneumatic connection  $G\frac{1}{2}$




Grade of filtration  $1\ \mu\text{m}$

MS9-LFM- $\frac{3}{4}$ /AGE, Pneumatic connection  $G\frac{3}{4}$




Grade of filtration  $1\ \mu\text{m}$

MS9-LFM-1/AGE, Pneumatic connection  $G1$




Grade of filtration  $1\ \mu\text{m}$

MS9-LFM-AGG, Pneumatic connection  $G1\frac{1}{4}$



Grade of filtration  $1\ \mu\text{m}$

MS9-LFM-AGH, Pneumatic connection  $G1\frac{1}{2}$



- 2 bar
  - - - 4 bar ( $q_{n\ min}$ : 289 l/min)
  - · - 6 bar ( $q_{n\ min}$ : 350 l/min)
  - · · 8 bar
  - - - 10 bar ( $q_{n\ min}$ : 450 l/min)
  - - - 12 bar
  - - - 14 bar ( $q_{n\ min}$ : 540 l/min)
  - - -  $q_{n\ max}$
- (with MS9-LFM-AGD:  $q_{n\ max}$ -values lie above the measured  $q_n$ -values)



## Fine and micro filters MS9-LFM, MS series

Technical data

### Standard flow rate $q_n$ as a function of the differential pressure $p_{1-2}$


Grade of filtration 0.01  $\mu\text{m}$

MS9-LFM- $\frac{3}{4}$ -...-HF, Pneumatic connection G $\frac{3}{4}$





Grade of filtration 0.01  $\mu\text{m}$

MS9-LFM-1-...-HF, Pneumatic connection G1




Grade of filtration 1  $\mu\text{m}$

MS9-LFM- $\frac{3}{4}$ -...-HF, Pneumatic connection G $\frac{3}{4}$



Grade of filtration 1  $\mu\text{m}$

MS9-LFM-1-...-HF, Pneumatic connection G1



**New**  
**Variant EX4, UL1**

**Fine and micro filters MS9-LFM, MS series**


Technical data

**FESTO**

**Dimensions – Basic version**  
without connecting thread G

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

without connecting thread G, with differential pressure indicator DA



Type	B1	B2	B3	L1		L2	L3	L5	L6
				Standard	High flow rate HF				
MS9-LFM-G	90	45	109	380.5	480.5	62	120	50	34.5
MS9-LFM-G-...-DA				405.5	505.5				

## Fine and micro filters MS9-LFM, MS series

Technical data


**FESTO**

### Dimensions – Connecting thread/connecting plate

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

with connecting thread 3/4 or 1

with connecting plate AG...



**2** Mounting screw M6xmin.90 to DIN 912 (not included in scope of delivery) for wall mounting without mounting bracket

**3** Earthing screw M4x8 (only with MS9-...-EX4)

→ Flow direction

Type	B4	B5	B6	B7		B8	D1	L4	L7		≅
					EX4					EX4	
MS9-LFM-3/4	90	104	91.5	-	-	-	G3/4	66	-	-	
MS9-LFM-1							G1				
MS9-LFM-AGD	-	-	-	112	122	132	G1/2	-	35	30	
MS9-LFM-AGE						132	G3/4			36	
MS9-LFM-AGF						142	G1			41	
MS9-LFM-AGG						162	G1 1/4			50	
MS9-LFM-AGH						176	G1 1/2			55	

Note: This product conforms to ISO 1179-1 and ISO 228-1

**New**  
**Variant EX4, UL1**

**Fine and micro filters MS9-LFM, MS series**


Technical data

**FESTO**

**Dimensions – Condensate drain**


Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Manual rotary M/fully automatic V



Barbed fitting for plastic tubing  
PCN-4


Semi-automatic H



QS connector for plastic tubing  
PUN-6/PAN-6

Fully automatic, electrically actuated E2/E3/E4

Technical data → Internet: [pwea](http://pwea)



Condensate drain PWEA:

- 2 Electrical connection: Screw terminal PG9
- 3 Connection 360° rotatable for plastic tubing PUN-H-12x2

Type	B1	D1	H1	L1	L2	L3
MS9-LFM-...-M/V	-	5	34.5	-	-	-
MS9-LFM-...-H		6				
MS9-LFM-...-E2/E3/E4	72	-	178	140	108	15

## Fine and micro filters MS9-LFM, MS series

**FESTO**

Technical data

Ordering data						
Without differential pressure indicator						
Size	Condensate drain	Connection	Micro filter		Fine filter	
			Grade of filtration 0.01 µm		Grade of filtration 1 µm	
			Part No.	Type	Part No.	Type
<b>Standard</b>						
MS9	Manual rotary	G $\frac{3}{4}$	553070	MS9-LFM- $\frac{3}{4}$ -AUM	553074	MS9-LFM- $\frac{3}{4}$ -BUM
		G1	553000	MS9-LFM-1-AUM	553004	MS9-LFM-1-BUM
		–	564047	MS9-LFM-G-AUM	564039	MS9-LFM-G-BUM
	Fully automatic	G $\frac{3}{4}$	553072	MS9-LFM- $\frac{3}{4}$ -AUV	553076	MS9-LFM- $\frac{3}{4}$ -BUV
		G1	553002	MS9-LFM-1-AUV	553006	MS9-LFM-1-BUV
		–	564049	MS9-LFM-G-AUV	564041	MS9-LFM-G-BUV
<b>High flow rate</b>						
MS9	Manual rotary	G $\frac{3}{4}$	552964	MS9-LFM- $\frac{3}{4}$ -AUM-HF	552968	MS9-LFM- $\frac{3}{4}$ -BUM-HF
		G1	553038	MS9-LFM-1-AUM-HF	553042	MS9-LFM-1-BUM-HF
		–	564051	MS9-LFM-G-AUM-HF	564043	MS9-LFM-G-BUM-HF
	Fully automatic	G $\frac{3}{4}$	552966	MS9-LFM- $\frac{3}{4}$ -AUV-HF	552970	MS9-LFM- $\frac{3}{4}$ -BUV-HF
		G1	553040	MS9-LFM-1-AUV-HF	553044	MS9-LFM-1-BUV-HF
		–	564053	MS9-LFM-G-AUV-HF	564045	MS9-LFM-G-BUV-HF

Ordering data						
With differential pressure indicator						
Size	Condensate drain	Connection	Micro filter		Fine filter	
			Grade of filtration 0.01 µm		Grade of filtration 1 µm	
			Part No.	Type	Part No.	Type
<b>Standard</b>						
MS9	Manual rotary	G $\frac{3}{4}$	553078	MS9-LFM- $\frac{3}{4}$ -AUM-DA	553082	MS9-LFM- $\frac{3}{4}$ -BUM-DA
		G1	553008	MS9-LFM-1-AUM-DA	553012	MS9-LFM-1-BUM-DA
		–	564048	MS9-LFM-G-AUM-DA	564040	MS9-LFM-G-BUM-DA
	Fully automatic	G $\frac{3}{4}$	553080	MS9-LFM- $\frac{3}{4}$ -AUV-DA	553084	MS9-LFM- $\frac{3}{4}$ -BUV-DA
		G1	553010	MS9-LFM-1-AUV-DA	553014	MS9-LFM-1-BUV-DA
		–	564050	MS9-LFM-G-AUV-DA	564042	MS9-LFM-G-BUV-DA
<b>High flow rate</b>						
MS9	Manual rotary	G $\frac{3}{4}$	552972	MS9-LFM- $\frac{3}{4}$ -AUM-HF-DA	552976	MS9-LFM- $\frac{3}{4}$ -BUM-HF-DA
		G1	553046	MS9-LFM-1-AUM-HF-DA	553050	MS9-LFM-1-BUM-HF-DA
		–	564052	MS9-LFM-G-AUM-HF-DA	564044	MS9-LFM-G-BUM-HF-DA
	Fully automatic	G $\frac{3}{4}$	552974	MS9-LFM- $\frac{3}{4}$ -AUV-HF-DA	552978	MS9-LFM- $\frac{3}{4}$ -BUV-HF-DA
		G1	553048	MS9-LFM-1-AUV-HF-DA	553052	MS9-LFM-1-BUV-HF-DA
		–	564054	MS9-LFM-G-AUV-HF-DA	564046	MS9-LFM-G-BUV-HF-DA

**New**  
**Variant EX4, UL1**

**Fine and micro filters MS9-LFM, MS series**



Ordering data – Modular products

**M** Mandatory data →

Module No.	Series	Size	Function	Connection size	Grade of filtration	Bowl
552940	MS	9	LFM	¾, 1, AGD, AGE, AGF, AGG, AGH, G	B, A	U
<b>Order example</b>						
552940	MS	9	- LFM	- AGD	- B	- U

**Ordering table**

Grid dimension	[mm]	90	Conditions	Code	Enter code
<b>M</b> Module No.	552940				
Series	Standard service unit			MS	MS
Size	9			9	9
Function	Fine and micro filter			-LFM	-LFM
Connection size	Thread G¾		1	-¾	
	Thread G1		1	-1	
	Connecting plate G½			-AGD	
	Connecting plate G¾			-AGE	
	Connecting plate G1			-AGF	
	Connecting plate G1¼			-AGG	
	Connecting plate G1½			-AGH	
	Module without connecting thread, without connecting plate		1	-G	
Grade of filtration	µm	1		-B	
		0.01		-A	
Bowl	Metal bowl			-U	-U

1 ¾, 1, G, E2, E3, E4, WPM

Not with EU certification EX4

Transfer order code

552940	MS	9	- LFM	-		-		- U
--------	----	---	-------	---	--	---	--	-----



## Fine and micro filters MS9-LFM, MS series

**FESTO**

Ordering data – Modular products

→ <b>M</b> Mandatory data		<b>O</b> Options				
<b>Condensate drain</b>	<b>Flow rate</b>	<b>Filter contamination sensor</b>	<b>Type of mounting</b>	<b>EU certification</b>	<b>UL certification</b>	<b>Alternative flow direction</b>
M, H, V, E2, E3, E4	HF	DA	WP, WPM, WPB	EX4	UL1	Z
- <b>M</b>	- <b>HF</b>	- <b>DA</b>	- <b>WP</b>	-	-	- <b>Z</b>

Ordering table						
Grid dimension	[mm]	90	Condition s	Code		Enter code
<b>M</b>	Condensate drain	Manual			-M	
		Semi-automatic (P1 max. 12 bar)			-H	
		Fully automatic (P1 max. 12 bar)			-V	
		External fully automatic condensate drain, electrical, 110 V AC, terminal strip		1	-E2	
		External fully automatic condensate drain, electrical, 230 V AC, terminal strip		1	-E3	
		External fully automatic condensate drain, electrical, 24 V DC, terminal strip		1	-E4	
<b>O</b>	Flow rate	High flow rate			-HF	
		Filter contamination sensor	Differential pressure indicator, visual		-DA	
	Type of mounting	Mounting bracket		2	-WP	
		Mounting bracket		1 2	-WPM	
		Wall mounting bracket for large wall gap		2	-WPB	
	EU certification	II 2GD to EU Directive 94/9/EG			-EX4	
	UL certification	cULus, ordinary location for Canada and USA			-UL1	
Alternative flow direction	Flow direction from right to left			-Z		

1 ¾, 1, G, E2, E3, E4, WPM

Not with EU certification EX4

2 WP, WPM, WPB


Not with module G

Transfer order code

-  -  -  -  -  -  -

## Activated carbon filters MS9-LFX, MS series

Peripherals overview



**Note**

Other accessories:

- Module connector for combination with size MS6, MS9 or MS12

→ Internet: [rmv, armv](#)

Mounting attachments and accessories					
		Individual device		Combination Module without connecting thread, without connecting plate G	→ Page/ Internet
		With female thread 3/4 or 1	With connecting plate AG...		
			Without EU certification EX4	With EU certification EX4	
1	Connecting plate MS9-AG...	-	■	■	ms9-ag
2	Module connector MS9-MV	-	-	■	ms9-mv
3	Mounting bracket MS9-WP	■	■	■	ms9-wp
4	Mounting bracket MS9-WPB	■	■	■	ms9-wp
5	Mounting bracket MS9-WPM	■	■	■	ms9-wp

## Activated carbon filters MS9-LFX, MS series

Type codes

		MS	9	-	LFX	-	¾	-	U
<b>Series</b>									
MS	Standard service unit								
<b>Size</b>									
9	Grid dimension 90 mm								
<b>Service function</b>									
LFX	Activated carbon filter								
<b>Pneumatic connection</b>									
¾	Thread G¾								
1	Thread G1								
G	Module without connecting thread, without connecting plate								
<b>Bowl guard</b>									
U	Integrated as metal bowl								


Further variants can be ordered using the modular system → 64

- Connecting plates
- Type of mounting
- EU certification
- UL certification
- Alternative flow direction

## Activated carbon filters MS9-LFX, MS series

**FESTO**

Technical data



Flow rate  
max. 6,500 l/min

Temperature range  
-10 ... +60 °C

Pressure  
0 ... 20 bar



- Removal of liquid and gaseous oil particles from compressed air using activated carbon
- Eliminates odours and vapours
- Prefiltration with micro filter MS9-LFM-A, grade of filtration 0.01 µm, recommended
- New filter cartridges → 88
- Optional device variant EX4 for use in potentially explosive areas in zones 1, 2, 21 and 22

General technical data				
Size	MS9			
Pneumatic connection 1, 2	G3/4	G1	G1/2 ... G1 1/2 (with connecting plate AG...)	- (without connecting thread G)
Constructional design	Activated carbon filter			
Type of mounting	Via accessories			
	In-line installation			
Installation position	Vertical ±5°			
Air purity class at the output <sup>1)</sup>	Compressed air in accordance with ISO 8573-1:2010 [1:4:2]			
Bowl guard	Integrated as metal bowl			
Residual oil content [mg/m <sup>3</sup> ]	≤0.003			

1) It is recommended to replace filter cartridges after 1,000 operating hours (applies to an ambient temperature of 21 °C). The service life of a filter cartridge is reduced at higher temperatures.

Note: This product conforms to ISO 1179-1 and ISO 228-1

Standard flow rate $q_n^{1)}$ [l/min]	
Max. standard flow rate for air purity class $q_n$ max	6,500

1) Measured at  $p_1 = 6$  bar

Operating and environmental conditions		
Operating pressure [bar]	0 ... 20	
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [1:4:2]	
Ambient temperature [°C]	-10 ... +60	
Temperature of medium [°C]	+5 ... +30	
Storage temperature [°C]	-10 ... +60	
Corrosion resistance class CRC <sup>2)</sup>	2	
Certification (variant UL1)	cULus recognized (OL)	

1) Corrosion resistance class 2 according to Festo standard 940 070  
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

## Activated carbon filters MS9-LFX, MS series

Technical data


**FESTO**

ATEX	
EU certification	EX4
ATEX category gas	II 2G
Ex-ignition protection type gas	c T6 X
ATEX category dust	II 2D
EX-ignition protection type dust	c 60 °C X
ATEX ambient temperature	-10 °C ≤ Ta ≤ +60 °C
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)

Weights [g]	
Activated carbon filter	2,000

### Materials


Sectional view




Activated carbon filter		
1	Housing	Die-cast aluminium
2	Bowl	Wrought aluminium alloy
	Inspection window	PA
3	Filter	Activated carbon
-	Cover	PA reinforced
-	Connecting plate, module connector, mounting bracket	Die-cast aluminium
-	Seals	NBR
	Note on materials	Free of copper and PTFE

### Standard flow rate $q_n$ as a function of the differential pressure $p_{1-2}$

MS9-LFX-AGD, Pneumatic connection G $\frac{1}{2}$



MS9-LFX- $\frac{3}{4}$ /AGE, Pneumatic connection G $\frac{3}{4}$



- 2 bar
- - - 4 bar
- · - 6 bar
- · · 8 bar
- - - - 10 bar
- - - - 12 bar
- · - · 14 bar


## Activated carbon filters MS9-LFX, MS series

Technical data


**FESTO**

### Standard flow rate $q_n$ as a function of the differential pressure $p_{1-2}$

MS9-LFX-1/AGF, Pneumatic connection G1



MS9-LFX-AGH, Pneumatic connection G1½




- 2 bar
- - - 4 bar
- · - 6 bar
- · · 8 bar
- - - - 10 bar
- · - · 12 bar
- · - · · 14 bar

### Dimensions – Basic version

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

without connecting thread G



1 Installation dimensions

→ Flow direction

Type	B1	B2	B3	L1	L2	L3	L5	L6
MS9-LFX-G	90	45	109	380.5	62	120	50	34.5

## Activated carbon filters MS9-LFX, MS series

Technical data


**FESTO**

### Dimensions – Connecting thread/connecting plate

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

with connecting thread  $\frac{3}{4}$  or 1

with connecting plate AG...



**2** Mounting screw M6xmin.90 to DIN 912 (not included in scope of delivery) for wall mounting without mounting bracket

**3** Earthing screw M4x8 (only with MS9-...-EX4)

→ Flow direction

Type	B4	B5	B6	B7		B8	D1	L4	L7		≅
					EX4					EX4	
MS9-LFX- $\frac{3}{4}$	90	104	91.5	-	-	-	G $\frac{3}{4}$	66	-	-	-
MS9-LFX-1							G1				
MS9-LFX-AGD	-	-	-	112	122	132	G $\frac{1}{2}$	-	35	-	30
MS9-LFX-AGE							G $\frac{3}{4}$				36
MS9-LFX-AGF							G1				41
MS9-LFX-AGG							G1 $\frac{1}{4}$				50
MS9-LFX-AGH							G1 $\frac{1}{2}$				55

Note: This product conforms to ISO 1179-1 and ISO 228-1

### Ordering data

Size	Connection	Part No.	Type
MS9	G $\frac{3}{4}$	552996	MS9-LFX- $\frac{3}{4}$ -U
	G1	553032	MS9-LFX-1-U
	-	564038	MS9-LFX-G-U

**New**  
**Variant EX4, UL1**

**Activated carbon filters MS9-LFX, MS series**

Ordering data – Modular products



M Mandatory data						O Options			
Module No.	Series	Size	Function	Connection size	Bowl	Type of mounting	EU certification	UL certification	Alternative flow direction
552942	MS	9	LFX	¾, 1, AGD, AGE, AGF, AGG, AGH, G	U	WP, WPM, WPB	EX4	UL1	Z
<b>Order example</b>									
552942	MS	9	- LFX	- AGD	- U	- WP			- Z

Ordering table					
Grid dimension	[mm]	90	Conditions	Code	Enter code
M	Module No.	552942			
	Series	Standard service unit		MS	MS
	Size	9		9	9
	Function	Activated carbon filter		-LFX	-LFX
	Connection size	Thread G¾	1	-¾	
		Thread G1	1	-1	
		Connecting plate G½		-AGD	
		Connecting plate G¾		-AGE	
		Connecting plate G1		-AGF	
		Connecting plate G1¼		-AGG	
		Connecting plate G1½		-AGH	
		Module without connecting thread, without connecting plate	1	-G	
	Bowl	Metal bowl		-U	-U
O	Type of mounting	Mounting bracket	2	-WP	
		Mounting bracket	1 2	-WPM	
		Wall mounting bracket for large wall gap	2	-WPB	
	EU certification	II 2GD to EU Directive 94/9/EG		-EX4	
	UL certification	cULus, ordinary location for Canada and USA		-UL1	
	Alternative flow direction	Flow direction from right to left		-Z	

- 1 ¾, 1, G, WPM Not with EU certification EX4
- 2 WP, WPM, WPB Not with module G


Transfer order code

552942	MS	9	- LFX	-	U	-	-	-	-	-
--------	----	---	-------	---	---	---	---	---	---	---



# Filters MS12-LF, MS series

Peripherals overview



**Note**  
 Additional accessories:  
 – Module connector for combination with size MS9 →  
 Internet: armv

Mounting attachments and accessories		→ Page/Internet
1	Connecting plate MS12-AG...	ms12-ag
2	Mounting bracket MS12-WP	ms12-wp
3	Module connector MS12-MV	ms12-mv
4	Condensate drain, fully automatic, electrically actuated E2/E3/E4	71

# Filters MS12-LF, MS series

Type codes

		MS	12	-	LF	-	G	-	C	U	V
<b>Series</b>											
MS	Standard service unit										
<b>Size</b>											
12	Grid dimension 124 mm										
<b>Service function</b>											
LF	Filter										
<b>Connection size</b>											
G	Module without connecting thread, without connecting plate Connecting plates → Accessories										
<b>Grade of filtration</b>											
C	5 µm										
E	40 µm										
<b>Bowl guard</b>											
U	Integrated as metal bowl										
<b>Condensate drain</b>											
V	Fully automatic										


Further variants can be ordered using the modular system → 71

- Connecting plates
- Condensate drain
- Type of mounting
- Alternative flow direction


# Filters MS12-LF, MS series

## Technical data

Function  
Condensate drain  
manual rotary



fully automatic



Flow rate  
11,500 ... 16,000 l/min  
Temperature range  
-10 ... +60 °C  
Pressure  
0.8 ... 20 bar



The sintered filter with centrifugal separation removes contamination, rust and condensate from the compressed air. The filter cartridges are replaceable.

- Good particle and condensate separation
- High flow rate with minimal pressure drop
- Available with manual, fully automatic or fully automatic, electrically actuated condensate drain
- Choice of filter cartridges: 5 µm or 40 µm
- New filter cartridges → 89

General technical data				
Pneumatic connection 1, 2 <sup>1)</sup>	G1	G1¼	G1½	G2
Design	Sintered filter with centrifugal separation			
Type of mounting	Via accessories In-line installation			
Assembly position	Vertical ±5°			
Grade of filtration [µm]	5 40			
Air purity class at the output	Compressed air in accordance with ISO 8573-1:2010 [6:8:4] (Grade of filtration 5 µm) Compressed air in accordance with ISO 8573-1:2010 [7:8:4] (Grade of filtration 40 µm)			
Bowl guard	Integrated as metal bowl			
Condensate drain	Manual rotary Fully automatic Fully automatic, electrical actuated			
Max. condensate volume [cm <sup>3</sup> ]	400			

1) Dependent on connecting plate selected, must be ordered separately as an accessory → Internet: ms12-ag

Note: This product conforms to ISO 1179-1 and ISO 228-1

Standard nominal flow rate qnN <sup>1)</sup> [l/min]					
Pneumatic connection	G1	G1¼	G1½	G2	
Grade of filtration	5 µm	11,500	12,500	13,500	14,000
	40 µm	12,500	13,000	14,000	16,000

1) Dependent on connecting plate selected, must be ordered separately as an accessory → Internet: ms12-ag

Measured at p<sub>1</sub> = 6 bar and Δp = 0.5 bar

# Filters MS12-LF, MS series

Technical data



Operating and environmental conditions			
Condensate drain	Manual rotary M	Fully automatic V	Fully automatic, electrical actuated E2/E3/E4
Operating pressure [bar]	0.8 ... 20	2 ... 12	0.8 ... 16
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [-:9:-]	Compressed air in accordance with ISO 8573-1:2010 [7:9:-]	Compressed air in accordance with ISO 8573-1:2010 [-:9:-]
	Inert gases		
Ambient temperature [°C]	-10 ... +60	+5 ... +60	+1 ... +60
Temperature of medium [°C]	-10 ... +60	+5 ... +60	+1 ... +60
Storage temperature [°C]	-10 ... +60	-10 ... +60	+1 ... +60
Corrosion resistance CRC <sup>1)</sup>	2		


1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Weights [g]	
Filter with metal bowl U	6,500
Filter with metal bowl U and fully automatic, electrically actuated condensate drain E2/E3/E4	7,200

## Materials

Sectional view



Filter		
1	Body	Die-cast aluminium
4	Metal bowl	Wrought aluminium alloy
5	Filter element	Sintered bronze
7	Spin disc	POM
8	Filter holder	POM
9	Separating plate	POM
10	Stabilising disc	POM
-	Seals	NBR



## Standard flow rate $q_n$ as a function of the differential pressure $\Delta p_{1-2}$

Grade of filtration 5  $\mu\text{m}$

$p_1 = 6 \text{ bar}$

With connecting plate MS12-AGF  
Pneumatic connection G1

With connecting plate MS12-AGI  
Pneumatic connection G2



# Filters MS12-LF, MS series

Technical data





## Standard flow rate $q_n$ as a function of the differential pressure $\Delta p_{1-2}$

Grade of filtration 40  $\mu\text{m}$

With connecting plate MS12-AGF  
Pneumatic connection G1


With connecting plate MS12-AGI  
Pneumatic connection G2

$p_1 = 6 \text{ bar}$



## Dimensions – Basic version

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)



Type	B1	B2	B3	B4	D5 Ø	L1	L2	L4	L5	L6
MS12-LF	124	122	61	148	40	458	86	166	250	16


# Filters MS12-LF, MS series

Technical data

**FESTO**


Dimensions – Condensate drain Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

**Manual rotary M**



Barbed fitting for plastic tubing  
PCN-4

**Fully automatic V**




Barbed fitting for plastic tubing  
PCN-4

Type	L6
MS12-LF-...-M	11

Type	L6
MS12-LF-...-V	13

Fully automatic, electrically actuated E2/E3/E4 Technical data → Internet: [pwea](http://pwea.com)



Condensate drain PWEA:

- 2 Electrical connection: Screw terminal PG9
- 3 Connection 360° rotatable for plastic tubing PUN-H-12x2

Ordering data						
Metal bowl						
Size	Condensate drain	Connection	Grade of filtration 5 µm		Grade of filtration 40 µm	
			Part No.	Type	Part No.	Type
MS12	fully automatic	G1 ... G2 <sup>1)</sup>	537152	MS12-LF-G-CUV	537151	MS12-LF-G-EUV

1) Connecting plate must be ordered separately as an accessory → Internet: [ms12-ag](http://ms12-ag.com)

Note: This product conforms to ISO 1179-1 and ISO 228-1

# Filters MS12-LF, MS series

Ordering data – Modular products

M Mandatory data								O Options	
Module No.	Series	Size	Function	Connection size	Grade of filtration	Bowl	Condensate drain	Type of mounting	Alternative flow direction
535023	MS	12	LF	AGF, AGG, AGH, AGI, G	E, C	U	M, V, E2, E3, E4	WP	Z
<b>Order example</b>									
535023	MS	12	- LF	- G	- E	- U	- V		

Ordering table					
Grid dimension	[mm]	124	Conditions	Code	Enter code
M	Module No.	535023			
	Series	Standard		MS	MS
	Size	12		12	12
	Function	Filter		-LF	-LF
	Connection size	Connecting plate G1		-AGF	
		Connecting plate G1 ¼		-AGG	
		Connecting plate G1 ½		-AGH	
		Connecting plate G2		-AGI	
		Module without connecting thread, without connecting plate		-G	
	Grade of filtration	40 µm		-E	
		5 µm		-C	
	Bowl	Metal bowl		-U	-U
	Condensate drain	Manual		-M	
		Fully automatic (P1 max. 12 bar)		-V	
		External fully automatic condensate drain, electrical, 110 V AC, terminals		-E2	
		External fully automatic condensate drain, electrical, 230 V AC, terminals		-E3	
		External fully automatic condensate drain, electrical, 24 V DC, terminals		-E4	
O	Type of mounting	Mounting bracket	1	-WP	
	Alternative flow direction	Flow direction from right to left		-Z	

1 WP Only with connecting plate AGF, AGG, AGH or AGI.


**Transfer order code**

535023	MS	12	- LF	-	-	- U	-	-	-	-
--------	----	----	------	---	---	-----	---	---	---	---

# Fine and micro filters MS12-LFM, MS series

Peripherals overview

**FESTO**



**Note**


Additional accessories:  
 – Module connector for combination with size MS9 →  
 Internet: armv

Mounting attachments and accessories		→ Page/Internet
1	Connecting plate MS12-AG...	ms12-ag
2	Mounting bracket MS12-WP	ms12-wp
3	Module connector MS12-MV	ms12-mv
4	Condensate drain, fully automatic, electrically actuated E2/E3/E4	80



# Fine and micro filters MS12-LFM, MS series

Type codes




Further variants can be ordered using the modular system → 80

- Connecting plates
- Condensate drain
- Filter change sensor
- Type of mounting
- Alternative flow direction


# Fine and micro filters MS12-LFM, MS series

Technical data


Function  
 Condensate drain  
 manual rotary  
 without differential pressure indicator




with differential pressure indicator



Condensate drain  
 fully automatic  
 without differential pressure indicator



with differential pressure indicator



Flow rate  
 500 ... 50,000 l/min  
 Temperature range  
 -10 ... +60 °C  
 Pressure  
 0.8 ... 20 bar



- High-performance filter for exceptionally clean compressed air
- Air quality to ISO 8573-1:2010
- Available with manual, fully automatic or fully automatic, electrically actuated condensate drain
- Available with differential pressure indicator for optical indication of filter contamination
- Choice of filter cartridges: 0.01 µm or 1 µm
- New filter cartridges → 89

General technical data				
Pneumatic connection 1, 2 <sup>1)</sup>	G1	G1¼	G1½	G2
Design	Fibre filter			
Type of mounting	Via accessories			
	In-line installation			
Assembly position	Vertical ±5°			
Grade of filtration [µm]	0.01 (micro filter MS12-LFM-A)			
	1 (fine filter MS12-LFM-B)			
Air purity class at the output	Compressed air in accordance with ISO 8573-1:2010 [1:7:2] (Grade of filtration 0.01µm, micro filter MS12-LFM-A)			
	Compressed air in accordance with ISO 8573-1:2010 [2:7:3] (Grade of filtration 1µm, fine filter MS12-LFM-B)			
Filter efficiency [%]	99.9999 (Grade of filtration 0.01µm, micro filter MS12-LFM-A)			
	99.99 (Grade of filtration 1µm, fine filter MS12-LFM-B)			
Bowl guard	Integrated as metal bowl			
Condensate drain	Manual rotary			
	Fully automatic			
	Fully automatic, electrical actuated			
Max. condensate volume [cm <sup>3</sup> ]	400			

1) Dependent on connecting plate selected, must be ordered separately as an accessory → Internet: ms12-ag

Note: This product conforms to ISO 1179-1 and ISO 228-1

# Fine and micro filters MS12-LFM, MS series

Technical data

Standard flow rate $q_n$ [l/min]				
Operating pressure	4 bar	6 bar	10 bar	14 bar
<b>Micro filter MS12-LFM-A</b>				
Max. standard flow rate for air purity class $q_{n \max}$	16,670	23,300	36,670	50,000
Min. standard flow rate for air purity class $q_{n \min}$	500	700	1,100	1,500
<b>Fine filter MS12-LFM-B</b>				
Max. standard flow rate for air purity class $q_{n \max}$	16,670	23,300	36,670	50,000
Min. standard flow rate for air purity class $q_{n \min}$	625	950	1,390	1,675

Operating and environmental conditions			
Condensate drain	Manual rotary M	Fully automatic V	Fully automatic, electrical actuated E2/E3/E4
Operating pressure [bar]	0.8 ... 20	2 ... 12	0.8 ... 16
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [6:8:4] <sup>1)</sup>		
	Inert gases		
Ambient temperature [°C]	-10 ... +60	+5 ... +60	+1 ... +60
Temperature of medium [°C]	-10 ... +60	+5 ... +60	+1 ... +60
Storage temperature [°C]	-10 ... +60	-10 ... +60	+1 ... +60
Corrosion resistance CRC <sup>2)</sup>	2		

1) It is recommended to prefilter the compressed air for the micro filter MS-LFM-A using a fine filter MS-LFM-B (grade of filtration 1 µm).


2) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Weights [g]	
Fine and micro filter with metal bowl U	7,000
Fine and micro filter with metal bowl U and fully automatic, electrically actuated condensate drain E2/E3/E4	7,700

## Materials

Sectional view



Fine and micro filter	
1	Body Die-cast aluminium
2	Metal bowl Wrought aluminium alloy
	Viewing window PC
3	Filter element Borosilicate mesh
-	Seals NBR
Note on materials	
RoHS-compliant (not with variant E2, E3 or E4)	
Free of copper and PTFE	

# Fine and micro filters MS12-LFM, MS series


Technical data



## Standard flow rate $q_n$ as a function of the differential pressure $p_{1-2}$


Grade of filtration 0.01  $\mu\text{m}$

With connecting plate MS12-AGF, Pneumatic connection G1




Grade of filtration 0.01  $\mu\text{m}$

With connecting plate MS12-AGG, Pneumatic connection G1¼




Grade of filtration 0.01  $\mu\text{m}$

With connecting plate MS12-AGH, Pneumatic connection G1½



Grade of filtration 0.01  $\mu\text{m}$

With connecting plate MS12-AGI, Pneumatic connection G2



- p1: 4 bar
- p1: 6 bar
- p1: 8 bar
- p1: 10 bar
- p1: 12 bar


# Fine and micro filters MS12-LFM, MS series

Technical data

## Standard flow rate $q_n$ as a function of the differential pressure $p_{1-2}$


Grade of filtration  $1\ \mu\text{m}$

With connecting plate MS12-AGF, Pneumatic connection G1




Grade of filtration  $1\ \mu\text{m}$

With connecting plate MS12-AGG, Pneumatic connection  $G1\frac{1}{4}$




Grade of filtration  $1\ \mu\text{m}$

With connecting plate MS12-AGH, Pneumatic connection  $G1\frac{1}{2}$



Grade of filtration  $1\ \mu\text{m}$

With connecting plate MS12-AGI, Pneumatic connection G2



- p1: 4 bar
- - - - - p1: 6 bar
- p1: 8 bar
- - - - - p1: 10 bar
- p1: 12 bar


# Fine and micro filters MS12-LFM, MS series

Technical data



## Dimensions – Basic version

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)



Type	B1	B2	B3	B4	D5 Ø	L1	L2	L4	L5	L6
MS12-LFM	124	122	61	148	40	543	86	166	350	16


# Fine and micro filters MS12-LFM, MS series

Technical data

**FESTO**

## Dimensions – Differential pressure indicator

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)




→ Flow direction

Type	B1	B2	B3	B4	L1	L2	L3
MS12-LFM-...-DA	124	122	61	148	569	112	192

## Dimensions – Condensate drain


Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

Manual rotary M



Barbed fitting for plastic tubing  
PCN-4

Fully automatic V




Barbed fitting for plastic tubing  
PCN-4

Type	L6
MS12-LFM-...-M	11

Type	L6
MS12-LFM-...-V	13

Fully automatic, electrically actuated E2/E3/E4

Technical data → Internet: [pwea](http://pwea)



Condensate drain PWEA:

- 2) Electrical connection: Screw terminal PG9
- 3) Connection 360° rotatable for plastic tubing PUN-H-12x2

## Ordering data

Metal bowl

Size	Condensate drain	Connection	Micro filter		Fine filter	
			Grade of filtration 0.01 µm	Part No.	Type	Grade of filtration 1 µm
MS12	fully automatic	G1 ... G2 <sup>1)</sup>	537154	MS12-LFM-G-AUV	537153	MS12-LFM-G-BUV

1) Connecting plate must be ordered separately as an accessory → Internet: [ms12-ag](http://ms12-ag)

Note: This product conforms to ISO 1179-1 and ISO 228-1

# Fine and micro filters MS12-LFM, MS series

Ordering data – Modular products

M Mandatory data								O Options		
Module No.	Series	Size	Function	Connection size	Grade of filtration	Bowl	Condensate drain	Filter change sensor	Type of mounting	Alternative flow direction
535042	MS	12	LFM	AGF, AGG, AGH, AGI, G	B, A	U	M, V, E2, E3, E4	DA	WP	Z
<b>Order example</b>										
535042	MS	12	- LFM	- AGI	- A	- U	- M	-	-	-

Ordering table		Grid dimension [mm]	124	Conditions	Code	Enter code
M	Module No.	535042				
	Series	Standard			MS	MS
	Size	12			12	12
	Function	Fine and micro filter			-LFM	-LFM
	Connection size	Connecting plate G1			-AGF	
		Connecting plate G1¼			-AGG	
		Connecting plate G1½			-AGH	
		Connecting plate G2			-AGI	
		Module without connecting thread, without connecting plate			-G	
	Grade of filtration	1 µm			-B	
		0.01 µm			-A	
	Bowl	Metal bowl			-U	-U
	Condensate drain	Manual			-M	
		Fully automatic (P1 max. 12 bar)			-V	
		External fully automatic condensate drain, electrical, 110 V AC, terminals			-E2	
		External fully automatic condensate drain, electrical, 230 V AC, terminals			-E3	
		External fully automatic condensate drain, electrical, 24 V DC, terminals			-E4	
O	Filter change sensor	Differential pressure indicator, optical			-DA	
	Type of mounting	Mounting bracket		1	-WP	
	Alternative flow direction	Flow direction from right to left			-Z	

1 WP Only with connecting plate AGF, AGG, AGH or AGI.


**Transfer order code**

535042	MS	12	- LFM	-	-	- U	-	-	-
--------	----	----	-------	---	---	-----	---	---	---



# Active carbon filters MS12-LFX, MS series

Peripherals overview




**Note**  
 Additional accessories:  
 – Module connector for combination with size MS9 →  
 Internet: armv

Mounting attachments and accessories		→ Page/Internet
1	Connecting plate MS12-AG...	ms12-ag
2	Mounting bracket MS12-WP	ms12-wp
3	Module connector MS12-MV	ms12-mv

# Active carbon filters MS12-LFX, MS series

Type codes




Further variants can be ordered using the modular system → 86

- Connecting plates
- Type of mounting
- Alternative flow direction

# Active carbon filters MS12-LFX, MS series

## Technical data

### Function



### Flow rate

5,065 ... 15,190 l/min

### Temperature range

-10 ... +60 °C

### Pressure

0 ... 20 bar



- Removal of liquid and gaseous oil particles from compressed air using active carbon
- Eliminates odours and vapours
- Prefiltration with micro filter MS12-LFM-A, grade of filtration 0.01 µm, recommended
- New filter cartridges → 89

General technical data				
Pneumatic connection 1, 2 <sup>1)</sup>	G1	G1¼	G1½	G2
Design	Active carbon filter			
Type of mounting	Via accessories			
	In-line installation			
Assembly position	Vertical ±5°			
Air purity class at the output <sup>2)</sup>	Compressed air in accordance with ISO 8573-1:2010 [1:4:1]			
Bowl guard	Integrated as metal bowl			
Residual oil content	[mg/m <sup>3</sup> ]	≤ 0.003		

1) Dependent on connecting plate selected, must be ordered separately as an accessory → Internet: ms12-ag

2) We recommend that the filter cartridge be replaced by a new one after 1,000 operating hours. (Applies to an ambient temperature of 21 °C. At higher temperatures the service life of the filter cartridge will be reduced.)

Note: This product conforms to ISO 1179-1 and ISO 228-1

Standard flow rate q <sub>n</sub> [l/min]				
Operating pressure	4 bar	6 bar	10 bar	14 bar
Max. standard flow rate for air purity class q <sub>n max</sub>	5,065	7,090	11,150	15,190

Operating and environmental conditions	
Operating pressure	[bar] 0 ... 20
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [1:4:2]
	Inert gases
Ambient temperature	[°C] -10 ... +60
Temperature of medium	[°C] +5 ... +30
Storage temperature	[°C] -10 ... +60
Corrosion resistance	CRC <sup>1)</sup> 2

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.


Weights [g]	
Active carbon filter with metal bowl U	7,000

# Active carbon filters MS12-LFX, MS series

Technical data

## Materials

Sectional view




### Active carbon filter


1	Body	Die-cast aluminium
4	Metal bowl	Wrought aluminium alloy
	Viewing window	PC
5	Filter	Active carbon
-	Seals	NBR
Note on materials		RoHS-compliant
		Free of copper and PTFE

### Standard flow rate $q_n$ as a function of the differential pressure $p_{1-2}$


With connecting plate MS12-AGF, Pneumatic connection G1




With connecting plate MS12-AGG, Pneumatic connection G1¼



With connecting plate MS12-AGH, Pneumatic connection G1½



With connecting plate MS12-AGI, Pneumatic connection G2




- $p_1$ : 4 bar
- - -  $p_1$ : 6 bar
- · -  $p_1$ : 8 bar
- · ·  $p_1$ : 10 bar
- - -  $p_1$ : 12 bar

# Active carbon filters MS12-LFX, MS series

Technical data

## Dimensions – Basic version

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)



1 Installation dimensions

→ Flow direction

Type	B1	B2	B3	B4	L1	L2	L4	L5
MS12-LFX	124	122	61	148	543	86	166	350

## Ordering data

Metal bowl

Size	Connection	Part No.	Type
MS12	G1 ... G2 <sup>1)</sup>	537155	MS12-LFX-G-U

1) Connecting plate must be ordered separately as an accessory → Internet: ms12-ag

Note: This product conforms to ISO 1179-1 and ISO 228-1

# Active carbon filters MS12-LFX, MS series

Ordering data – Modular products

M Mandatory data						O Options	
Module No.	Series	Size	Function	Connection size	Bowl	Type of mounting	Alternative flow direction
535043	MS	12	LFX	AGF AGG AGH AGI G	U	WP	Z
<b>Order example</b>							
535043	MS	12	LFX	AGF	U	WP	Z

Ordering table								
Grid dimension		[mm]	124			Condition s	Code	Enter code
M	Module No.	535043						
	Series	Standard					MS	MS
	Size	12					12	12
	Function	Active carbon filter					-LFX	-LFX
	Connection size	Connecting plate G1					-AGF	
		Connecting plate G1 ¼					-AGG	
		Connecting plate G1 ½					-AGH	
		Connecting plate G2					-AGI	
		Module without connecting thread, without connecting plate					-G	
	Bowl	Metal bowl					-U	-U
O	Type of mounting	Mounting bracket				1	-WP	
	Alternative flow direction	Flow direction from right to left					-Z	

1 WP Only with connecting plate AGF, AGG, AGH or AGI.

Transfer order code

535043	MS	12	-	LFX	-		-	U	-		-	
--------	----	----	---	-----	---	--	---	---	---	--	---	--

# Filters MS-LF/LFM/LFX, MS series

Accessories

## Filter cartridges, MS4/MS6 series



Ordering data				
Size	Filter cartridge	Grade of filtration [µm]	Part No.	Type
MS4	Micro-filter cartridge	0.01	162674	MS4/D-MINI-LFM-A
	Fine-filter cartridge	1	162677	MS4/D-MINI-LFM-B
	Filter cartridge (colour: blue)	5	534501	MS4-LFP-C
	Filter cartridge (colour: white)	40	534502	MS4-LFP-E
	Activated carbon filter cartridge	–	532912	MS4/D-MINI-LFX
MS6	Micro-filter cartridge	0.01	532909	MS6-LFM-A
	Fine-filter cartridge	1	532910	MS6-LFM-B
	Filter cartridge (colour: blue)	5	534499	MS6-LFP-C
	Filter cartridge (colour: white)	40	534500	MS6-LFP-E
	Activated carbon filter cartridge	–	532911	MS6-LFX
High flow rate HF				
MS6	Micro-filter cartridge	0.01	552093	MS6-LFM-A-HF
	Fine-filter cartridge	1	552092	MS6-LFM-B-HF
	Activated carbon filter cartridge	–	552094	MS6-LFX-HF
Range of application HP, suitable for sealing air and cleaning air				
MS6	Micro-filter cartridge	0,01	547922	MS6-LFM-AI
	Fine-filter cartridge	1	547923	MS6-LFM-BI
	Activated carbon filter cartridge	–	547925	MS6-LFX-AKI

## Filters MS-LF/LFM/LFX, MS series

Accessories

FESTO

Filter cartridges, MS9 series



Ordering data				
Size	Filter cartridge	Grade of filtration [µm]	Part No.	Type
MS9	Micro-filter cartridge	0.01	553036	MS9-LFM-A
	Fine-filter cartridge	1	553037	MS9-LFM-B
	Filter cartridge	5	570309	MS9-LFP-C
	Filter cartridge	40	570310	MS9-LFP-E
	Activated carbon filter cartridge	–	552946	MS9-LFX
High flow rate HF				
MS9	Micro-filter cartridge	0.01	552944	MS9-LFM-A-HF
	Fine-filter cartridge	1	552945	MS9-LFM-B-HF




## Filters MS-LF/LFM/LFX, MS series

FESTO

Accessories

Filter cartridges, MS12 series



Ordering data				
Size	Filter cartridge	Grade of filtration [µm]	Part No.	Type
MS12	Micro-filter cartridge	0.01	537146	MS12-LFM-A
	Fine-filter cartridge	1	537145	MS12-LFM-B
	Filter cartridge	5	537143	MS12-LFP-C
	Filter cartridge	40	537144	MS12-LFP-E
	Activated carbon filter cartridge	-	537147	MS12-LFX

# Product Range and Company Overview

## A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



**Custom Automation Components**  
Complete custom engineered solutions



**Custom Control Cabinets**  
Comprehensive engineering support and on-site services



**Complete Systems**  
Shipment, stocking and storage services

## The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



**Electromechanical**  
Electromechanical actuators, motors, controllers & drives



**Pneumatics**  
Pneumatic linear and rotary actuators, valves, and air supply



**PLCs and I/O Devices**  
PLC's, operator interfaces, sensors and I/O devices

## Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

## Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

# Festo North America

## Festo Regional Contact Center

5300 Explorer Drive  
Mississauga, Ontario L4W 5G4  
Canada

### USA Customers:

For ordering assistance,

**Call:** 1.800.99.FESTO (1.800.993.3786)

**Fax:** 1.800.96.FESTO (1.800.963.3786)

**Email:** [customer.service@us.festo.com](mailto:customer.service@us.festo.com)

For technical support,

**Call:** 1.866.GO.FESTO (1.866.463.3786)

**Fax:** 1.800.96.FESTO (1.800.963.3786)

**Email:** [product.support@us.festo.com](mailto:product.support@us.festo.com)

### Canadian Customers:

**Call:** 1.877.GO.FESTO (1.877.463.3786)

**Fax:** 1.877.FX.FESTO (1.877.393.3786)

**Email:** [festo.canada@ca.festo.com](mailto:festo.canada@ca.festo.com)

---

## USA Headquarters

Festo Corporation  
395 Moreland Road  
P.O. Box 18023  
Hauppauge, NY 11788, USA  
[www.festo.com/us](http://www.festo.com/us)

---

## USA Sales Offices

### Appleton

North 922 Tower View Drive, Suite N  
Greenville, WI 54942, USA

### Boston

120 Presidential Way, Suite 330  
Woburn, MA 01801, USA

### Chicago

1441 East Business Center Drive  
Mt. Prospect, IL 60056, USA

### Dallas

1825 Lakeway Drive, Suite 600  
Lewisville, TX 75057, USA

### Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320  
Auburn Hills, MI 48326, USA

### New York

395 Moreland Road  
Hauppauge, NY 11788, USA

### Silicon Valley

4935 Southfront Road, Suite F  
Livermore, CA 94550, USA

## United States



**USA Headquarters, East:** Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: [info@festo-usa.com](mailto:info@festo-usa.com)

[www.festo.com/us](http://www.festo.com/us)

## Canada



**Headquarters:** Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: [festo.canada@ca.festo.com](mailto:festo.canada@ca.festo.com)

[www.festo.ca](http://www.festo.ca)

## Mexico



**Headquarters:** Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,  
54020 Tlalneantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: [festo.mexico@mx.festo.com](mailto:festo.mexico@mx.festo.com)

[www.festo.com/mx](http://www.festo.com/mx)

---

## Central USA

Festo Corporation  
1441 East Business  
Center Drive  
Mt. Prospect, IL 60056, USA  
Phone: 1.847.759.2600  
Fax: 1.847.768.9480



## Western USA

Festo Corporation  
4935 Southfront Road,  
Suite F  
Livermore, CA 94550, USA  
Phone: 1.925.371.1099  
Fax: 1.925.245.1286



---

## Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark  
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia  
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore  
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

[www.festo.com](http://www.festo.com)