


Swivel/linear drive units DSL-B

FESTO



Swivel/linear drive units DSL-B


Key features

FESTO

At a glance

- High repetition accuracy thanks to cushioning components with fixed stop
- Swivel angle can be infinitely and accurately set
- The mechanical gearing between the stop element and swivel module prevents movement of the stop system under load
- Compact sensing of the swivel motion via proximity sensors SME/SMT-10F
- With plain-bearing guide
- With recirculating ball bearing guide
- Swivel motion of up to 270°
- Linear motion of up to 200 mm stroke
- Both motion types can be controlled individually or simultaneously
- High rotational energy during swivelling thanks to directly mounted, self-adjusting shock absorbers
- Supply ports at one end for quick, clear-cut tubing connections
- High precision thanks to recirculating ball bearing guide
 - Backlash-free swivel motion
 - Resists torque loads even during linear motion

The technology in detail



1 Cushioning	2 Position sensing	3 Sensor retainer	4 Stop lever
• Choice of two types of cushioning, each with metal fixed stop: – Flexible cushioning elements – Hydraulic shock absorbers	• Compact sensing of the swivel position using proximity sensors SME/SMT-10F	• The proximity sensors are mounted directly on the stop system. The sensor retainer can be ordered as an accessory	• The magnet in the stop lever enables the swivel angle to be sensed
5 Piston rod	6 Slot for proximity sensor	7 Precision end position adjustment	8 Angle scale
Mounting interface, for example for a gripper	• Compact sensing of the linear position using proximity sensors SME/SMT-8	• After the lock nut is loosened, precision adjustment of the end positions is possible using an Allen key	• The required angle can easily be preset using the scale

Mounting options

Direct mounting	Flange mounting	Flange mounting	Via slot nuts
	For size 16: The mounting thread on the bearing cap complies with DIN ISO 6432.	For sizes 20 ... 40: Mounting hole pattern to DIN ISO 6431, VDMA 24 562 and NF E 49 003.1.	

Swivel/linear drive units DSL-B

FESTO


Type codes

		DSL	–	25	–	80	–	270	–	P	–	A	–	S2	–	KF	–	B
Type																		
Double-acting																		
DSL	Swivel/linear drive unit																	
Size																		
Stroke [mm]																		
Swivel angle																		
270	270°																	
End position cushioning																		
P	Flexible cushioning components at both ends																	
CC	Shock absorbers at both ends																	
Position sensing																		
A	Via proximity sensor																	
Piston rod																		
S2	Through piston rod																	
S20	Through, hollow piston rod																	
Guide																		
	Plain-bearing guide																	
KF	Recirculating ball bearing guide																	
Generation																		
B	B series																	

Swivel/linear drive units DSL-B

Peripherals overview

FESTO




Accessories			
	Brief description	➔ Page/Internet	
1	Cushioning mount DSM-B • For flexible cushioning components • For shock absorbers	18	
2	Shock absorber DYSC	Self-adjusting shock absorbers with fixed stop	18
3	Cushioning kit DSM-...-P-B	Flexible cushioning components with fixed stop	18
4	Sensor retainer SL-DSM-B	For mounting proximity sensors SME/SMT-10	19
5	Proximity sensor SME/SMT-10F	For sensing the swivel position	19
6	Cover cap AKM	Reduces the risk of injury in the swivel range of the stop lever	18
7	Flange mounting FBN	For bearing cap of swivel/linear unit DSL-16	16
8	Flange mounting FNG	For bearing cap of swivel/linear units DSL-20 ... 40	16
9	Push-on flange FWSR	For retrofitting the swivel/linear unit DSL	17
10	Slot nut NST	For mounting the drive via the linear part	17
11	Slot cover ABP	To protect the proximity sensor cable and keep dirt out of the sensor/profile slots	20
12	Proximity sensor SME/SMT-8	For sensing the linear position	19
13	One-way flow control valve GRLA	For regulating speed	18
14	Push-in fitting QS	For connecting compressed air tubing with standard outside diameter	quick star

Swivel/linear drive units DSL-B


Technical data

FESTO

Function




Variants



S2

S20

www.festo.com/en/Spare_parts_service



-N- Size
16 ... 40 mm

-T- Stroke length
10 ... 200 mm

Force
1.25 ... 20 Nm

General technical data							
Size			16	20	25	32	40
Pneumatic connection			M5			G1/8	
Constructional design			Vane-driven semi-rotary actuator in combination with a double-acting linear cylinder				
Cushioning	Swivel motion		P – Flexible cushioning components at both ends CC – Shock absorbers at both ends				
	Linear motion		P – Not adjustable at either end				
Max. swivel angle	with cushioning P	[°]	270	270	270	270	270
	with cushioning CC	[°]	246	246	246	246	240
Max. swivel angle backlash ¹⁾	with plain-bearing guide	[°]	2				
	with recirculating ball bearing guide	[°]	0.05				
Swivel angle adjustment ²⁾	with cushioning P	[°]	–6				
	with cushioning CC	[°]	–3				
Max. perm. swivel frequency ³⁾	with cushioning P	[Hz]	2	2	2	2	2
	with cushioning CC	[Hz]	1.5	1	1	0.7	0.7
Stroke	with plain-bearing guide	[mm]	10 ... 160			10 ... 200	
	with recirculating ball bearing guide	[mm]	10 ... 100				10 ... 160
Max. impact velocity		[mm/s]	500				
Repetition accuracy of swivel motion	with cushioning P	[°]	1				
	with cushioning CC	[°]	0.1				
Position sensing			Via proximity sensor				
Type of mounting			Clamped in T-slot				
			Via external thread				
Mounting position			Any				

- 1) In new condition
2) Per side
3) At max. swivel angle

Swivel/linear drive units DSL-B

Technical data

FESTO

Operating and environmental conditions		
Operating medium		Filtered compressed air, lubricated or unlubricated
Operating pressure	[bar]	2.5 ... 8
Ambient temperature ¹⁾	[°C]	-10 ... +60
Corrosion resistance class CRC ²⁾		1


1) Note operating range of proximity sensors.

2) Corrosion resistance class 1 as per Festo standard 940 070

Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

Forces and torques						
Size		16	20	25	32	40
Theoretical torque ¹⁾	[Nm]	1.25	2.5	5	10	20
Theoretical force, advancing ¹⁾	with plain-bearing guide	[N]	102.5	159	246	422.5
	with recirculating ball bearing guide	[N]	103.5	158	248	403.5
Theoretical force, retracting ¹⁾	[N]	73.5	120.5	173.5	294	495
Max. perm. effective load → 7	[kg]	1	3	6	9	14

1) Theoretical values at 6 bar

Observe max. dynamic torque load (linear motion)						
Size		16	20	25	32	40
	with plain-bearing guide	[Nm]	0.1	0.2	0.45	0.8
	with recirculating ball bearing guide	[Nm]	0.17	0.35	0.7	1.0
						5.4

Note

The rotary vane is not suitable for use in defining end positions, i.e. the stop lever and the stops must not be removed.

With plain-bearing guide:

If the effective load is attached eccentrically, increased internal friction forces occur with horizontal installation, thereby causing a reduction of the effective force of the linear motion.

Weight [g]					
Size	16	20	25	32	40
Plain-bearing guide					
Cushioning P	695	1,090	1,510	2,985	5,150
Cushioning CC	697	1,130	1,605	3,020	5,205
Additional weight per 10 mm stroke	33	52	67	109	170
Recirculating ball bearing guide					
Cushioning P	745	1,180	1,660	3,265	5,300
Cushioning CC	747	1,220	1,755	3,300	5,355
Additional weight per 10 mm stroke	33	52	67	109	175


Swivel/linear drive units DSL-B

Technical data

FESTO

Materials


Sectional view




Swivel/linear drive unit

1	Cylinder barrel, housing	Wrought aluminium alloy, smooth anodised
2	Piston rod, shaft	Stainless steel, nickel plated
3	Rotary vane	Glass fibre reinforced plastic
4	Stop lever	Anodised aluminium
5	Piston	Brass
-	Fixed stops, shock absorber retainer	Stainless steel
-	Seals	Polyurethane

Lateral force F_q as a function of stroke length l





- Piston rod with bearings at both ends
- Resists high torques and lateral forces



— $\varnothing 16$
 - - $\varnothing 20$
 - · - $\varnothing 25$
 · · · $\varnothing 32$
 - - - $\varnothing 36$
 - - - $\varnothing 40$

Max. permissible effective load as a function of piston speed v



— $\varnothing 16$
 - - $\varnothing 20$
 - · - $\varnothing 25$
 · · · $\varnothing 32$
 - - - $\varnothing 36$
 - - - $\varnothing 40$


Swivel/linear drive units DSL-B

Technical data


FESTO

Max. permissible mass moment of inertia J as a function of swivel time t


DSL-16-...-P




DSL-16-...-CC




DSL-20-...-P




DSL-20-...-CC



DSL-25-...-P



DSL-25-...-CC



— 90°
 - - - 180°
 - · - 270°


Swivel/linear drive units DSL-B

Technical data


FESTO

Max. permissible mass moment of inertia J as a function of swivel time t


DSL-32-...-P




DSL-32-...-CC



DSL-40-...-P



DSL-40-...-CC



— 90°
 - - - 180°
 - · - 270°

In the graphs for the types DSL-...-CC, the swivel time is shown up to the point when the stop lever meets the shock absorber. The cushioning time of the shock absorber must be added in order to obtain total swivel time.

Cushioning time of the shock absorber

Size	16/20/25	32	40
Cushioning time [s]	0.1	0.25	0.3

Note

Sizing software
 Calculating inertia
 → www.festo.com


Swivel/linear drive units DSL-B

Technical data

FESTO

Dimensions

Download CAD Data → www.festo.com/us/cad



Swivel/linear drive units DSL-B

Technical data

FESTO

Size	AM	B Ø d11	D1 Ø g7	D2 Ø f8	D3 ¹⁾		D4		D5	D6 Ø ±0.2	D7	D8
					S2	S20	S2	S20				
16	20 ^{+0.2}	–	8	10	M3	M3	M3	M3	M8x1	58	–	M2
20	23 ^{+0.2}	30	10	12	M5	M5	M5	M5	M10x1	69	M6	M2
25	30 ^{+0.2}	35	12	16	M5	M5	M5	M5	M10x1	82	M6	M2
32	40 ^{+0.3}	40	16	20	M5	M5	M5	M5	M12x1	104	M8	M2
40	50 ^{+0.3}	45	20	25	M6	G ¹ / ₈	M6	M7	M16x1	128	M8	M2

Size	D11 ¹⁾	E	EE	H1 max.	H2	H3	L1 ¹⁾	L2 ±0.2	L3	L4
16	–	38	M5	8.8	4.6	23.7	89 ^{+1.1/-1.3}	6	22.5 ^{+0.5}	9 ⁺²
20	–	50	M5	11.2	8.1	27.7	95 ^{+1.1/-1.3}	6	26.2 ^{+0.6}	10 ⁺¹
25	–	57	M5	13.5	4	22	100.5 ^{+1.2/-1.3}	6	29.5 ^{+0.6}	10 ⁺¹
32	–	72	G ¹ / ₈	18	6	30.5	111 ^{+1.3/-1.4}	9	39.5 ^{+0.6}	12.5 ⁺²
40	–	83.5	G ¹ / ₈	22.5	5.7	45.5	132 ^{+1.3/-1.4}	9	44.7 ^{+0.6}	6.5 ⁺²

Size	L5	L6 +2	L7	L8 ±0.3	L10 ¹⁾	TG	VD	WH	ZB ¹⁾
16	18 ^{+0.2}	–	9 ⁺²	–	159 ^{+0.8/-0.1}	–	22 ^{+0.2}	28 ^{+1.3/-1.7}	144.8 ^{+1.4/-1.5}
20	26 ^{–0.2}	17	10 ⁺¹	10.5	175 ^{+0.8/-0.1}	32.5	19 ^{+0.2}	26 ^{+1.3/-1.7}	161.8 ^{+1.4/-1.5}
25	27.5 ^{–0.2}	17	10 ⁺¹	10.5	186.5 ^{+0.8/-0.1}	38	21.5 ^{+0.2}	30 ^{+1.4/-1.7}	173.4 ^{+1.4/-1.2}
32	28.5 ^{–0.2}	21	12.5 ⁺²	12	224 ^{+0.6/-0.2}	46.5	28.5 ^{+0.3}	37 ^{+1.4/-1.8}	205 ^{+1.5/-1.9}
40	35 ^{–0.2}	18	14 ⁺²	15	263 ^{+0.6/-0.2}	56.5	34.7 ^{+0.3}	46 ^{+1.4/-1.8}	243.5 ^{+1.8/-1.9}

Size	α	≈C1	≈C2	≈C3	≈C4	Woodruff key to DIN 6885	D10 min. Ø S20
16	60°	10	5.5	2.5	2.5	A2x2x16	2.5
20	50°	13	7	3	3	A3x3x18	3.2
25	50°	13	9	4	3	A4x4x25	4.2
32	50°	15	10	5	4	A5x5x36	4.2
40	50°	19	12	8	5	A6x6x45	5.6

1) Deviating dimensions for variant with recirculating ball bearing guide KF

Size	Stroke	D3	D11 Ø h7	L1	L11		ZB
					S2 +0.8/-0.1	S20 +0.8/-0.1	
16	25	M3	6	104 ^{+1.1/-1.3}	*	198	159.6 ^{+1.4/-1.5}
	≤ 50				*	233	
	> 50				213	273	
20	≤ 50	M5	8	111 ^{+1.1/-1.3}	*	241	177.7 ^{+1.4/-1.5}
	> 50				225	291	
25	≤ 50	M5	10	129 ^{+1.2/-1.3}	*	266	201.2 ^{+1.4/-1.2}
	> 50				238	316	
32	≤ 50	M7	13	143 ^{+1.3/-1.4}	*	305	237 ^{+1.5/-1.9}
	> 50				253	355	
40	≤ 50	G ¹ / ₈	16	182 ^{+1.3/-1.4}	*	364	293.5 ^{+1.5/-1.9}
	> 50				*	414	
	> 100				352	464	

*) Profile rod does not protrude beyond the drive unit

Swivel/linear drive units DSL-B

Technical data

FESTO

Ordering data – With recirculating ball bearing guide							
Version	Size	Stroke [mm]	P – Flexible cushioning components at both ends			CC – Shock absorbers at both ends	
			Part No.	Type		Part No.	Type
S2 – Through piston rod							
	16	25	556 390	DSL-16-25-270-P-A-S2-B		556 391	DSL-16-25-270-CC-A-S2-B
		40	556 396	DSL-16-40-270-P-A-S2-B		556 397	DSL-16-40-270-CC-A-S2-B
		50	556 402	DSL-16-50-270-P-A-S2-B		556 403	DSL-16-50-270-CC-A-S2-B
		80	556 408	DSL-16-80-270-P-A-S2-B		556 409	DSL-16-80-270-CC-A-S2-B
		100	556 414	DSL-16-100-270-P-A-S2-B		556 415	DSL-16-100-270-CC-A-S2-B
		10 ... 160	556 420	DSL-16-...-270-P-A-S2-B		556 421	DSL-16-...-270-CC-A-S2-B
	20	25	556 426	DSL-20-25-270-P-A-S2-B		556 427	DSL-20-25-270-CC-A-S2-B
		40	556 432	DSL-20-40-270-P-A-S2-B		556 433	DSL-20-40-270-CC-A-S2-B
		50	556 438	DSL-20-50-270-P-A-S2-B		556 439	DSL-20-50-270-CC-A-S2-B
		80	556 444	DSL-20-80-270-P-A-S2-B		556 445	DSL-20-80-270-CC-A-S2-B
		100	556 450	DSL-20-100-270-P-A-S2-B		556 451	DSL-20-100-270-CC-A-S2-B
		10 ... 160	556 456	DSL-20-...-270-P-A-S2-B		556 457	DSL-20-...-270-CC-A-S2-B
	25	25	556 462	DSL-25-25-270-P-A-S2-B		556 463	DSL-25-25-270-CC-A-S2-B
		40	556 468	DSL-25-40-270-P-A-S2-B		556 469	DSL-25-40-270-CC-A-S2-B
		50	556 474	DSL-25-50-270-P-A-S2-B		556 475	DSL-25-50-270-CC-A-S2-B
		80	556 480	DSL-25-80-270-P-A-S2-B		556 481	DSL-25-80-270-CC-A-S2-B
		100	556 486	DSL-25-100-270-P-A-S2-B		556 487	DSL-25-100-270-CC-A-S2-B
		10 ... 160	556 492	DSL-25-...-270-P-A-S2-B		556 493	DSL-25-...-270-CC-A-S2-B
	32	25	556 498	DSL-32-25-270-P-A-S2-B		556 499	DSL-32-25-270-CC-A-S2-B
		40	556 504	DSL-32-40-270-P-A-S2-B		556 505	DSL-32-40-270-CC-A-S2-B
		50	556 510	DSL-32-50-270-P-A-S2-B		556 511	DSL-32-50-270-CC-A-S2-B
		80	556 516	DSL-32-80-270-P-A-S2-B		556 517	DSL-32-80-270-CC-A-S2-B
		100	556 522	DSL-32-100-270-P-A-S2-B		556 523	DSL-32-100-270-CC-A-S2-B
		10 ... 200	556 528	DSL-32-...-270-P-A-S2-B		556 529	DSL-32-...-270-CC-A-S2-B
	40	25	556 534	DSL-40-25-270-P-A-S2-B		556 535	DSL-40-25-270-CC-A-S2-B
		40	556 540	DSL-40-40-270-P-A-S2-B		556 541	DSL-40-40-270-CC-A-S2-B
		50	556 546	DSL-40-50-270-P-A-S2-B		556 547	DSL-40-50-270-CC-A-S2-B
		80	556 552	DSL-40-80-270-P-A-S2-B		556 553	DSL-40-80-270-CC-A-S2-B
		100	556 558	DSL-40-100-270-P-A-S2-B		556 559	DSL-40-100-270-CC-A-S2-B
		125	556 564	DSL-40-125-270-P-A-S2-B		556 565	DSL-40-125-270-CC-A-S2-B
		160	556 570	DSL-40-160-270-P-A-S2-B		556 571	DSL-40-160-270-CC-A-S2-B
		10 ... 200	556 576	DSL-40-...-270-P-A-S2-B		556 577	DSL-40-...-270-CC-A-S2-B

Swivel/linear drive units DSL-B

Technical data

FESTO

Ordering data – With recirculating ball bearing guide							
Version	Size	Stroke [mm]	P – Flexible cushioning components at both ends			CC – Shock absorbers at both ends	
			Part No.	Type		Part No.	Type
S20 – Through, hollow piston rod							
	16	25	556 393	DSL-16-25-270-P-A-S20-B		556 394	DSL-16-25-270-CC-A-S20-B
		40	556 399	DSL-16-40-270-P-A-S20-B		556 400	DSL-16-40-270-CC-A-S20-B
		50	556 405	DSL-16-50-270-P-A-S20-B		556 406	DSL-16-50-270-CC-A-S20-B
		80	556 411	DSL-16-80-270-P-A-S20-B		556 412	DSL-16-80-270-CC-A-S20-B
		100	556 417	DSL-16-100-270-P-A-S20-B		556 418	DSL-16-100-270-CC-A-S20-B
		10 ... 160	556 423	DSL-16-...-270-P-A-S20-B		556 424	DSL-16-...-270-CC-A-S20-B
	20	25	556 429	DSL-20-25-270-P-A-S20-B		556 430	DSL-20-25-270-CC-A-S20-B
		40	556 435	DSL-20-40-270-P-A-S20-B		556 436	DSL-20-40-270-CC-A-S20-B
		50	556 441	DSL-20-50-270-P-A-S20-B		556 442	DSL-20-50-270-CC-A-S20-B
		80	556 447	DSL-20-80-270-P-A-S20-B		556 448	DSL-20-80-270-CC-A-S20-B
		100	556 453	DSL-20-100-270-P-A-S20-B		556 454	DSL-20-100-270-CC-A-S20-B
		10 ... 160	556 459	DSL-20-...-270-P-A-S20-B		556 460	DSL-20-...-270-CC-A-S20-B
	25	25	556 465	DSL-25-25-270-P-A-S20-B		556 466	DSL-25-25-270-CC-A-S20-B
		40	556 471	DSL-25-40-270-P-A-S20-B		556 472	DSL-25-40-270-CC-A-S20-B
		50	556 477	DSL-25-50-270-P-A-S20-B		556 478	DSL-25-50-270-CC-A-S20-B
		80	556 483	DSL-25-80-270-P-A-S20-B		556 484	DSL-25-80-270-CC-A-S20-B
		100	556 489	DSL-25-100-270-P-A-S20-B		556 490	DSL-25-100-270-CC-A-S20-B
		10 ... 160	556 495	DSL-25-...-270-P-A-S20-B		556 496	DSL-25-...-270-CC-A-S20-B
	32	25	556 501	DSL-32-25-270-P-A-S20-B		556 502	DSL-32-25-270-CC-A-S20-B
		40	556 507	DSL-32-40-270-P-A-S20-B		556 508	DSL-32-40-270-CC-A-S20-B
		50	556 513	DSL-32-50-270-P-A-S20-B		556 514	DSL-32-50-270-CC-A-S20-B
		80	556 519	DSL-32-80-270-P-A-S20-B		556 520	DSL-32-80-270-CC-A-S20-B
		100	556 525	DSL-32-100-270-P-A-S20-B		556 526	DSL-32-100-270-CC-A-S20-B
		10 ... 200	556 531	DSL-32-...-270-P-A-S20-B		556 532	DSL-32-...-270-CC-A-S20-B
	40	25	556 537	DSL-40-25-270-P-A-S20-B		556 538	DSL-40-25-270-CC-A-S20-B
		40	556 543	DSL-40-40-270-P-A-S20-B		556 544	DSL-40-40-270-CC-A-S20-B
		50	556 549	DSL-40-50-270-P-A-S20-B		556 550	DSL-40-50-270-CC-A-S20-B
		80	556 555	DSL-40-80-270-P-A-S20-B		556 556	DSL-40-80-270-CC-A-S20-B
		100	556 561	DSL-40-100-270-P-A-S20-B		556 562	DSL-40-100-270-CC-A-S20-B
		125	556 567	DSL-40-125-270-P-A-S20-B		556 568	DSL-40-125-270-CC-A-S20-B
		160	556 573	DSL-40-160-270-P-A-S20-B		556 574	DSL-40-160-270-CC-A-S20-B
		10 ... 200	556 579	DSL-40-...-270-P-A-S20-B		556 580	DSL-40-...-270-CC-A-S20-B

Swivel/linear drive units DSL-B

Technical data

FESTO

Ordering data – With recirculating ball bearing guide							
Version	Size	Stroke [mm]	P – Flexible cushioning components at both ends			CC – Shock absorbers at both ends	
			Part No.	Type		Part No.	Type
S2 – Through piston rod							
	16	25	556 582	DSL-16-25-270-P-A-S2-KF-B		556 583	DSL-16-25-270-CC-A-S2-KF-B
		40	556 588	DSL-16-40-270-P-A-S2-KF-B		556 589	DSL-16-40-270-CC-A-S2-KF-B
		50	556 594	DSL-16-50-270-P-A-S2-KF-B		556 595	DSL-16-50-270-CC-A-S2-KF-B
		80	556 600	DSL-16-80-270-P-A-S2-KF-B		556 601	DSL-16-80-270-CC-A-S2-KF-B
		100	556 606	DSL-16-100-270-P-A-S2-KF-B		556 607	DSL-16-100-270-CC-A-S2-KF-B
		10 ... 100	556 612	DSL-16-...-270-P-A-S2-KF-B		556 613	DSL-16-...-270-CC-A-S2-KF-B
	20	25	556 618	DSL-20-25-270-P-A-S2-KF-B		556 619	DSL-20-25-270-CC-A-S2-KF-B
		40	556 624	DSL-20-40-270-P-A-S2-KF-B		556 625	DSL-20-40-270-CC-A-S2-KF-B
		50	556 630	DSL-20-50-270-P-A-S2-KF-B		556 631	DSL-20-50-270-CC-A-S2-KF-B
		80	556 636	DSL-20-80-270-P-A-S2-KF-B		556 637	DSL-20-80-270-CC-A-S2-KF-B
		100	556 642	DSL-20-100-270-P-A-S2-KF-B		556 643	DSL-20-100-270-CC-A-S2-KF-B
		10 ... 100	556 648	DSL-20-...-270-P-A-S2-KF-B		556 649	DSL-20-...-270-CC-A-S2-KF-B
	25	25	556 654	DSL-25-25-270-P-A-S2-KF-B		556 655	DSL-25-25-270-CC-A-S2-KF-B
		40	556 660	DSL-25-40-270-P-A-S2-KF-B		556 661	DSL-25-40-270-CC-A-S2-KF-B
		50	556 666	DSL-25-50-270-P-A-S2-KF-B		556 667	DSL-25-50-270-CC-A-S2-KF-B
		80	556 672	DSL-25-80-270-P-A-S2-KF-B		556 673	DSL-25-80-270-CC-A-S2-KF-B
		100	556 678	DSL-25-100-270-P-A-S2-KF-B		556 679	DSL-25-100-270-CC-A-S2-KF-B
		10 ... 100	556 684	DSL-25-...-270-P-A-S2-KF-B		556 685	DSL-25-...-270-CC-A-S2-KF-B
	32	25	556 690	DSL-32-25-270-P-A-S2-KF-B		556 691	DSL-32-25-270-CC-A-S2-KF-B
		40	556 696	DSL-32-40-270-P-A-S2-KF-B		556 697	DSL-32-40-270-CC-A-S2-KF-B
		50	556 702	DSL-32-50-270-P-A-S2-KF-B		556 703	DSL-32-50-270-CC-A-S2-KF-B
		80	556 708	DSL-32-80-270-P-A-S2-KF-B		556 709	DSL-32-80-270-CC-A-S2-KF-B
		100	556 714	DSL-32-100-270-P-A-S2-KF-B		556 715	DSL-32-100-270-CC-A-S2-KF-B
		10 ... 100	556 720	DSL-32-...-270-P-A-S2-KF-B		556 721	DSL-32-...-270-CC-A-S2-KF-B
	40	25	556 726	DSL-40-25-270-P-A-S2-KF-B		556 727	DSL-40-25-270-CC-A-S2-KF-B
		40	556 732	DSL-40-40-270-P-A-S2-KF-B		556 733	DSL-40-40-270-CC-A-S2-KF-B
		50	556 738	DSL-40-50-270-P-A-S2-KF-B		556 739	DSL-40-50-270-CC-A-S2-KF-B
		80	556 744	DSL-40-80-270-P-A-S2-KF-B		556 745	DSL-40-80-270-CC-A-S2-KF-B
		100	556 750	DSL-40-100-270-P-A-S2-KF-B		556 751	DSL-40-100-270-CC-A-S2-KF-B
		125	556 756	DSL-40-125-270-P-A-S2-KF-B		556 757	DSL-40-125-270-CC-A-S2-KF-B
		160	556 762	DSL-40-160-270-P-A-S2-KF-B		556 763	DSL-40-160-270-CC-A-S2-KF-B
		10 ... 160	556 768	DSL-40-...-270-P-A-S2-KF-B		556 769	DSL-40-...-270-CC-A-S2-KF-B

Swivel/linear drive units DSL-B

Technical data

FESTO

Ordering data – With recirculating ball bearing guide							
Version	Size	Stroke [mm]	P – Flexible cushioning components at both ends			CC – Shock absorbers at both ends	
			Part No.	Type		Part No.	Type
S20 – Through, hollow piston rod							
	16	25	556 585	DSL-16-25-270-P-A-S20-KF-B		556 586	DSL-16-25-270-CC-A-S20-KF-B
		40	556 591	DSL-16-40-270-P-A-S20-KF-B		556 592	DSL-16-40-270-CC-A-S20-KF-B
		50	556 597	DSL-16-50-270-P-A-S20-KF-B		556 598	DSL-16-50-270-CC-A-S20-KF-B
		80	556 603	DSL-16-80-270-P-A-S20-KF-B		556 604	DSL-16-80-270-CC-A-S20-KF-B
		100	556 609	DSL-16-100-270-P-A-S20-KF-B		556 610	DSL-16-100-270-CC-A-S20-KF-B
		10 ... 100	556 615	DSL-16-...-270-P-A-S20-KF-B		556 616	DSL-16-...-270-CC-A-S20-KF-B
	20	25	556 621	DSL-20-25-270-P-A-S20-KF-B		556 622	DSL-20-25-270-CC-A-S20-KF-B
		40	556 627	DSL-20-40-270-P-A-S20-KF-B		556 628	DSL-20-40-270-CC-A-S20-KF-B
		50	556 633	DSL-20-50-270-P-A-S20-KF-B		556 634	DSL-20-50-270-CC-A-S20-KF-B
		80	556 639	DSL-20-80-270-P-A-S20-KF-B		556 640	DSL-20-80-270-CC-A-S20-KF-B
		100	556 645	DSL-20-100-270-P-A-S20-KF-B		556 646	DSL-20-100-270-CC-A-S20-KF-B
		10 ... 100	556 651	DSL-20-...-270-P-A-S20-KF-B		556 652	DSL-20-...-270-CC-A-S20-KF-B
	25	25	556 657	DSL-25-25-270-P-A-S20-KF-B		556 658	DSL-25-25-270-CC-A-S20-KF-B
		40	556 663	DSL-25-40-270-P-A-S20-KF-B		556 664	DSL-25-40-270-CC-A-S20-KF-B
		50	556 669	DSL-25-50-270-P-A-S20-KF-B		556 670	DSL-25-50-270-CC-A-S20-KF-B
		80	556 675	DSL-25-80-270-P-A-S20-KF-B		556 676	DSL-25-80-270-CC-A-S20-KF-B
		100	556 681	DSL-25-100-270-P-A-S20-KF-B		556 682	DSL-25-100-270-CC-A-S20-KF-B
		10 ... 100	556 687	DSL-25-...-270-P-A-S20-KF-B		556 688	DSL-25-...-270-CC-A-S20-KF-B
	32	25	556 693	DSL-32-25-270-P-A-S20-KF-B		556 694	DSL-32-25-270-CC-A-S20-KF-B
		40	556 699	DSL-32-40-270-P-A-S20-KF-B		556 700	DSL-32-40-270-CC-A-S20-KF-B
		50	556 705	DSL-32-50-270-P-A-S20-KF-B		556 706	DSL-32-50-270-CC-A-S20-KF-B
		80	556 711	DSL-32-80-270-P-A-S20-KF-B		556 712	DSL-32-80-270-CC-A-S20-KF-B
		100	556 717	DSL-32-100-270-P-A-S20-KF-B		556 718	DSL-32-100-270-CC-A-S20-KF-B
		10 ... 100	556 723	DSL-32-...-270-P-A-S20-KF-B		556 724	DSL-32-...-270-CC-A-S20-KF-B
	40	25	556 729	DSL-40-25-270-P-A-S20-KF-B		556 730	DSL-40-25-270-CC-A-S20-KF-B
		40	556 735	DSL-40-40-270-P-A-S20-KF-B		556 736	DSL-40-40-270-CC-A-S20-KF-B
		50	556 741	DSL-40-50-270-P-A-S20-KF-B		556 742	DSL-40-50-270-CC-A-S20-KF-B
		80	556 747	DSL-40-80-270-P-A-S20-KF-B		556 748	DSL-40-80-270-CC-A-S20-KF-B
		100	556 753	DSL-40-100-270-P-A-S20-KF-B		556 754	DSL-40-100-270-CC-A-S20-KF-B
		125	556 759	DSL-40-125-270-P-A-S20-KF-B		556 760	DSL-40-125-270-CC-A-S20-KF-B
		160	556 765	DSL-40-160-270-P-A-S20-KF-B		556 766	DSL-40-160-270-CC-A-S20-KF-B
		10 ... 160	556 771	DSL-40-...-270-P-A-S20-KF-B		556 772	DSL-40-...-270-CC-A-S20-KF-B

Swivel/linear drive units DSL-B

Accessories


FESTO

Flange mounting FBN

Material:

Galvanised steel

Free of copper, PTFE and silicone



Dimensions and ordering data										
For size	E	FB Ø H13	MF	TF	UF	W1	CRC ¹⁾	Weight [g]	Part No.	Type
16	40	6.6	5	50	66	23	2	52	5 131	FBN-20/25

1) Corrosion resistance class 2 as per Festo standard 940 070



Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Flange mounting FNG

Material:

Galvanised steel

Free of copper, PTFE and silicone



Dimensions and ordering data										
For size	E	FB Ø H13	MF	R	TF	UF	W1	CRC ¹⁾	Weight [g]	Part No. Type
20	45	7	10	32	64	80	16	1	221	32 940 FNG-32
25	54	9	10	36	72	90	20	1	291	32 941 FNG-40
32	65	9	12	45	90	110	25	1	536	32 942 FNG-50
40	75	9	12	50	100	120	34	1	679	32 943 FNG-63

1) CRC1: Corrosion resistance class to Festo standard 940070

Components with light corrosion exposure. Protection for transport and storage. Components without significant decorative function or surface, e.g. installed out of sight internally or behind covers.

Swivel/linear drive units DSL-B

FESTO


Accessories

Slot nut NST

Material:

Tempered steel, non-alloyed

Free of copper, PTFE and silicone



Dimensions and ordering data							
For size	D1	L1	L2	CRC ¹⁾	Weight [g]	Part No.	Type
16	M5	12	4	2	3	150 914	NST-5-M5
20							
25	M6	22.5	6.25	2	11	150 915	NST-8-M6
32							
40							

1) Corrosion resistance class 2 as per Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.


Push-on flange FWSR

The permissible tightening torque must not be exceeded when attaching additional components to the spigot shaft.

Material:

Wrought aluminium alloy, anodised

Free of copper, PTFE and silicone



Dimensions and ordering data														
For size	B5	D11 H13 Ø	D12 f8 Ø	D13 Ø	D14 Ø	D15	L11	L12	L13	Tightening torque [Nm]	CRC ¹⁾	Weight [g]	Part No.	Type
16	25	3.4	14	15	35	M3	25	3	3	1.2	2	21	14 659	FWSR-12
20	28	4.5	16	17	40	M4	28	5	6	5.5	2	32	170 153	FWSR-16-M5
25	35	5.5	20	23	50	M5	38	8	3	5.5	2	70	170 154	FWSR-25-M5
32	45	6.6	28	28	60	M6	48	10	4	5.5	2	127	13 241	FWSR-32
40	54	9	36	38	70	M8	60	11	5	10	2	240	14 656	FWSR-40

1) Corrosion resistance class 2 as per Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.



Swivel/linear drive units DSL-B

Accessories

FESTO

Cover cap AKM

Material:
Polyamide



Dimensions and ordering data				
For size	D1 Ø	L1	Part No.	Type
16	59	56.2±1.2	549 194	AKM-12
20	70	68±1.2	549 195	AKM-16
25	83	73.4±1.2	549 196	AKM-25
32	105	89.7±1.5	549 197	AKM-32
40	130	107.1±1.5	549 198	AKM-40

Ordering data – Cushioning kits				
	For size	Remarks	Part No.	Type
	16	For cushioning mount DSM-...-B	550 657	DSM-12-P-B
	20, 25		550 658	DSM-16/25-P-B
	32		550 659	DSM-32-P-B
	40		550 660	DSM-40-P-B

Ordering data – Shock absorbers			Technical data → Internet: dysc	
	For size	Remarks	Part No.	Type
	16	For cushioning mount DSM-...-B	548 011	DYSC-5-5-Y1F
	20, 25		548 012	DYSC-7-5-Y1F
	32		548 013	DYSC-8-8-Y1F
	40		548 014	DYSC-12-12-Y1F

Ordering data – Cushioning mounts				
	For size	Remarks	Part No.	Type
	16	- For flexible cushioning components - For shock absorbers	547 900	DSM-12-B
	20		547 901	DSM-16-B
	25		547 902	DSM-25-B
	32		547 903	DSM-32-B
	40		547 904	DSM-40-B

Ordering data – One-way flow control valves				Technical data → Internet: grla	
	Connection		Material	Part No.	Type
	Thread	For tubing O.D.			
For exhaust air					
	M5	3	Metal design	193 137	GRLA-M5-QS-3-D
		4		193 138	GRLA-M5-QS-4-D
		6		193 139	GRLA-M5-QS-6-D
	G1/8	3		193 142	GRLA-1/8-QS-3-D
		4		193 143	GRLA-1/8-QS-4-D
		6		193 144	GRLA-1/8-QS-6-D
		8		193 145	GRLA-1/8-QS-8-D

Swivel/linear drive units DSL-B

Accessories


FESTO

Ordering data – Sensor retainer				
	For size	Remarks	Part No.	Type
	16, 20, 25, 32, 40	Can only be used in combination with proximity sensors SME-/SMT-10F	550 661	SL-DSM-B

Ordering data – Proximity sensors for C-slot, magneto-resistive					Technical data → Internet: smt-10	
	Type of mounting	Switching output	Electrical connection, connection direction	Cable length [m]	Part No.	Type
N/O contact						
	Is clamped to the DSM using the sensor retainer	PNP	Cable, 3-wire, in-line	2.5	525 915	SMT-10F-PS-24V-K2,5L-OE
			Plug M8x1, 3-pin, in-line	0.3	525 916	SMT-10F-PS-24V-K0,3L-M8D

Ordering data – Proximity sensors for C-slot, magnetic reed					Technical data → Internet: sme-10	
	Type of mounting	Switching output	Electrical connection, connection direction	Cable length [m]	Part No.	Type
N/O contact						
	Is clamped to the DSM using the sensor retainer	Contacting	Plug M8x1, 3-pin, in-line	0.3	525 914	SME-10F-DS-24V-K0,3L-M8D
			Cable, 3-wire, in-line	2.5	525 913	SME-10F-DS-24V-K2,5L-OE
			Cable, 2-wire, in-line	2.5	526 672	SME-10F-ZS-24V-K2,5L-OE

Ordering data – Proximity sensors for T-slot, magneto-resistive					Technical data ➔ Internet: smt-8	
	Type of mounting	Switching output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above, flush with the cylinder profile	PNP	Cable, 3-wire	2.5	543 867	SMT-8M-PS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 866	SMT-8M-PS-24V-K-0,3-M8D
			Plug M12x1, 3-pin	0.3	543 869	SMT-8M-PS-24V-K-0,3-M12
		NPN	Cable, 3-wire	2.5	543 870	SMT-8M-NS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 871	SMT-8M-NS-24V-K-0,3-M8D
	Insertable in the slot lengthwise, flush with the cylinder profile	PNP	Cable, 3-wire	2.5	175 436	SMT-8-PS-K-LED-24-B
			Plug M8x1, 3-pin	0.3	175 484	SMT-8-PS-S-LED-24-B
N/C contact						
	Insertable in the slot from above, flush with the cylinder profile	PNP	Cable, 3-wire	7.5	543 873	SMT-8M-PO-24V-K7,5-OE

Ordering data – Proximity sensors for T-slot, magnetic reed					Technical data ➔ Internet: sme-8	
	Type of mounting	Switching output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above, flush with the cylinder profile	Contacting	Cable, 3-wire	2.5	543 862	SME-8M-DS-24V-K-2,5-OE
				5.0	543 863	SME-8M-DS-24V-K-5,0-OE
			Cable, 2-wire	2.5	543 872	SME-8M-ZS-24V-K-2,5-OE
				Plug M8x1, 3-pin	0.3	543 861
	Insertable in the slot lengthwise, flush with the cylinder profile	Contacting	Cable, 3-wire	2.5	150 855	SME-8-K-LED-24
			Plug M8x1, 3-pin	0.3	150 857	SME-8-S-LED-24
N/C contact						
	Insertable in the slot lengthwise, flush with the cylinder profile	Contacting	Cable, 3-wire	7.5	160 251	SME-8-O-K-LED-24

Swivel/linear drive units DSL-B

Accessories

FESTO

Ordering data – Connecting cables				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 333	NEBU-M8G3-K-2.5-LE3
			5	541 334	NEBU-M8G3-K-5-LE3
	Straight socket, M12x1, 5-pin	Cable, open end, 3-wire	2.5	541 363	NEBU-M12G5-K-2.5-LE3
			5	541 364	NEBU-M12G5-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 338	NEBU-M8W3-K-2.5-LE3
			5	541 341	NEBU-M8W3-K-5-LE3
	Angled socket, M12x1, 5-pin	Cable, open end, 3-wire	2.5	541 367	NEBU-M12W5-K-2.5-LE3
			5	541 370	NEBU-M12W5-K-5-LE3

Ordering data – Slot covers for T-slot					
	For Ø	Application	Assembly	Length [m]	Part No. Type
	16 ... 40	For sensor slots	Insertable from above	2x 0.5	151 680 ABP-5-S
	16, 20	For profile slots	Insertable from above	2x 0.5	151 681 ABP-5
	25 ... 40				151 682 ABP-8

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com