

One-way flow control valves

FESTO







One-way flow control valves

Key features

FESTO





Function		
Flow control or one-way flow control valves regulate the piston speed of pneumatic drives during advance and return strokes. This is done through suitable restriction of the flow rate of compressed air in exhaust air or supply air direction. With the one-way	flow control valve GRLA or GRLZ, the flow control function works in one direction only (exhaust air or supply air); the non-return function works in the opposite direction. With the flow control valve GRLO, the flow control function is active in both directions.	The flow control function creates an adjustable annular gap inside the valve. This gap can be increased or decreased by turning the knurled screw or slotted head screw. The required restriction can be set with the help of this adjustment component.
		Note The documentation for the flow control valves can be found at www.festo.com/catalogue

General information		
Standard nominal flow rate q_{nN}	Exhaust air one-way flow control function	Flow measurement circuit
The standard nominal flow rate q_{nN} is the flow rate based on standard conditions at an operating pressure of $p_1 = 6$ bar and an output pressure of $p_2 = 5$ bar, measured at room temperature $t = 20$ °C.		
Standard flow rate q_n	Supply air one-way flow control function	p_1 Operating pressure p_2 Output pressure
The standard flow rate is measured at an operating pressure of $p_1 = 6$ bar and an output pressure with respect to atmospheric pressure ($p_2 = 0$ bar).		 1 Supply port (pneumatic connection 1) 2 Working line (pneumatic connection 2)
	Flow control function in both directions	
		

One-way flow control valves

Key features

FESTO

Flow control functions and range of applications			
Application	Description	Application	Description
Double-acting cylinder with one-way flow control valve			
Exhaust air one-way flow control function		Supply air one-way flow control function	
	Speed adjustment through exhaust air flow control. Uncontrolled supply air and controlled exhaust air move the piston between air cushions (improves motion, even with load changes).		Adjustable speed during advance and return strokes. The flow rate is identical in both directions.
Single-acting cylinder with one-way flow control valve		Single-acting cylinder with flow control valve	
Exhaust air and supply air one-way flow control function		Flow control function in both directions	
	Adjustable speed during advance and return strokes. The flow rate can be adjusted differently for both directions.		Speed adjustment through flow control on both sides is often applied in the case of single-acting or small cylinders. The benefit of this application lies in its simplicity.


Application examples

Mini slide SLT with one-way flow control valve, standard

Flat cylinder DZF with one-way flow control valve, mini

Multimount cylinder DMM with one-way flow control valve, mini




Gripper HGW with one-way flow control valve, mini



One-way flow control valves

Product range overview

FESTO

Version	Valve function	Version	Type	Connection direction	Pneumatic connection 1	Pneumatic connection 2	qnN ¹⁾ [l/min]	Adjustment component	➔ Page/ Internet				
Standard	Metal												
	Exhaust air one-way flow control function		GRLA	Elbow outlet	QS-3, QS-4, QS-6, QS-8, QS-10, QS-12	M5, G1/8, G1/4, G3/8, G1/2	100 ... 1,580	Slotted head screw	8				
								Knurled screw					
									M5, G1/8, G1/4, G3/8, G1/2, G3/4	M5, G1/8, G1/4, G3/8, G1/2, G3/4	95 ... 4,320	Slotted head screw	12
									M5, G1/8, G1/4	M5, G1/8, G1/4	95 ... 610	Knurled screw	
			PK-3, PK-4, PK-6	M5, G1/8, G1/4	83 ... 540	Slotted head screw	12						
			GRLSA	Elbow outlet	QS-6	G1/8	0 ... 250	Rotary knob with scale, internal hex	17				
	Supply air one-way flow control function		GRLZ	Elbow outlet	QS-3, QS-4, QS-6, QS-8	M5, G1/8	100 ... 215	Slotted head screw	8				
									M5, G1/8, G1/4	M5, G1/8, G1/4	95 ... 610	Slotted head screw	12
									Knurled screw				
			PK-3, PK-4, PK-6	M5, G1/8, G1/4	83 ... 540	Slotted head screw	12						
			VFOC-S	Elbow outlet	QS-4, QS-6	Push-in sleeve ²⁾ QS-4, QS-6	100 ... 270	Slotted head screw	20				
Chromed metal													
Exhaust air one-way flow control function		GRLA-F	Elbow outlet	QS-4, QS-6, QS-8	G1/8, G1/4	180 ... 530	Slotted head screw	22					
Polymer													
Exhaust air one-way flow control function		GRLA	Elbow outlet	QS-6, QS-8	G1/8, G1/4, G3/8	520 ... 650	Knurled screw	24					


1) Standard nominal flow rate in direction of flow control.

2) Only suitable for push-in connector QS.

One-way flow control valves

Product range overview

FESTO

Version	Valve function	Version	Type	Connection direction	Pneumatic connection 1	Pneumatic connection 2	q _N ¹⁾ [l/min]	Adjustment component	→ Page/ Internet
Mini	Metal								
	Exhaust air one-way flow control function		GRLA	Elbow outlet	QS-3, QS-4	M3, M5	40 ... 41	Slotted head screw	26
					M3	M3	0 ... 18	Slotted head screw	29
	Supply air one-way flow control function		GRGA	Parallel outlet	QS-3	M3	0 ... 41	Slotted head screw	26
			GRLZ	Elbow outlet	QS-3, QS-4	M3, M5	41 ... 48	Slotted head screw	26
					M3	M3	0 ... 18	Slotted head screw	29
			GRGZ	Parallel outlet	QS-3	M3	0 ... 41	Slotted head screw	26
In-line installation	Metal								
	One-way flow control function		GR/GRA	Inline	M3, M5, G ¹ / ₈ , G ¹ / ₄ , G ³ / ₈ , G ¹ / ₂ , G ³ / ₄	M3, M5, G ¹ / ₈ , G ¹ / ₄ , G ³ / ₈ , G ¹ / ₂ , G ³ / ₄	29.5 ... 3,300	Knurled screw	gr
	Polymer								
	One-way flow control function		GR	Inline	QS-3, QS-4, QS-6, QS-8	QS-3, QS-4, QS-6, QS-8	25 ... 225	Knurled screw	gr
Corrosion-resistant	Stainless steel								
	Exhaust air one-way flow control function		CRGRLA	Elbow outlet	M5, G ¹ / ₈ , G ¹ / ₄ , G ³ / ₈ , G ¹ / ₂	M5, G ¹ / ₈ , G ¹ / ₄ , G ³ / ₈ , G ¹ / ₂	95 ... 2,100	Slotted head screw	31
Function combination	Metal								
	Exhaust air one-way flow control function		GRXA	–	QS-4, QS-6, QS-8	G ¹ / ₈ , G ¹ / ₄	130 ... 280	Slotted head screw	34

1) Standard nominal flow rate in direction of flow control.

One-way flow control valves

Type codes

FESTO

GRLA/GRLSA/GRLA-F/GRGA/CRGRLA/GRLZ/GRGZ

GRLA - 1/8 - QS - 6 - - - D

Type	
Exhaust air one-way flow control function	
GRLA	One-way flow control valve, elbow outlet
GRLSA	One-way flow control valve, elbow outlet with rotary knob
GRLA-F	One-way flow control valve, elbow outlet, chromed metal
GRGA	One-way flow control valve, parallel outlet
CRGRLA	One-way flow control valve, elbow outlet, corrosion-resistant
GRXA-HG	One-way flow control valve, function combination
Supply air one-way flow control function	
GRLZ	One-way flow control valve, elbow outlet
GRGZ	One-way flow control valve, parallel outlet
Pneumatic connection 2	
M3, M5, 1/8, 1/4, 3/8, 1/2, 3/4	Male thread
Pneumatic connection 1	
Connection type	
-	Female thread (connection size as for connection 2)
QS	Push-in connector QS
PK	Barbed connector
Tubing O.D. or tubing I.D.	
3, 4, 6, 8, 10, 12	Tubing O.D. with push-in connector QS
3, 4, 6	Tubing I.D. with barbed connector PK
Adjustment component	
-	Slotted head screw
RS	Knurled screw
Flow rate characteristic	
LF	Low flow
MF	Medium flow
Generation	
B	B series
C	C series
D	D series

One-way flow control valves

Type codes



VOFC	
Type	
VOFC	One-way flow control valve, elbow outlet
Valve function	
S	Supply air one-way flow control function
Pneumatic connection 2	
S4	Push-in sleeve QS-4
S6	Push-in sleeve QS-6
Pneumatic connection 1	
Q4	Push-in connector QS-4
Q6	Push-in connector QS-6

VOFC

-

S

-

S6

-

Q6

One-way flow control valves GRLA/GRLZ, standard



FESTO

Technical data – Push-in connector QS, metal

One-way flow control function

Exhaust air

Supply air



Flow rate

100 ... 1,580 l/min

Temperature range

-10 ... +60 °C

Pressure

0.2 ... 10 bar

- Can be swivelled 360° around the screw-in axis after mounting




General technical data – GRLA					
Valve function	Exhaust air one-way flow control function				
Pneumatic connection 2	M5	G1/8	G1/4	G3/8	G1/2
Pneumatic connection 1	QS-3, QS-4, QS-6	QS-3, QS-4, QS-6, QS-8	QS-6, QS-8, QS-10	QS-6, QS-8, QS-10	QS-12
Adjustment component	Slotted head screw Knurled screw				
Type of mounting	Screw-in, via male thread				
Mounting position	Any				
Max. tightening torque [Nm]	1.5	5	11	15	18

General technical data – GRLZ	
Valve function	Supply air one-way flow control function
Pneumatic connection 2	M5 G1/8
Pneumatic connection 1	QS-3, QS-4, QS-6 QS-3, QS-4, QS-6, QS-8
Adjustment component	Slotted head screw
Type of mounting	Screw-in, via male thread
Mounting position	Any
Max. tightening torque [Nm]	1.5 5

Operating and environmental conditions	
Operating pressure [bar]	0.2 ... 10
Operating medium	Dried compressed air, lubricated or unlubricated, grade of filtration 40 µm
Ambient temperature [°C]	-10 ... +60
Temperature of medium [°C]	-10 ... +60
Storage temperature [°C]	-10 ... +40
Certification	Germanischer Lloyd

Standard nominal flow rate q_{nN} at 6 → 5 bar
as a function of turns of the adjusting screw n


GRLA/GRLZ-M5



Standard flow rate q_n at 6 → 0 bar

as a function of turns of the adjusting screw n

GRLA/GRLZ-M5




One-way flow control valves GRLA/GRLZ, standard

FESTO

Technical data – Push-in connector QS, metal


Standard nominal flow rate q_{pN} at 6 $\rightarrow$ 5 bar
as a function of turns of the adjusting screw n

GRLA/GRLZ-1/8




Standard flow rate q_n at 6 $\rightarrow$ 0 bar
as a function of turns of the adjusting screw n


GRLA/GRLZ-1/8




GRLA-1/8-...-MF/GRLA-1/4




GRLA-1/8-...-MF/GRLA-1/4




GRLA-3/8




GRLA-3/8



GRLA-1/2



GRLA-1/2




One-way flow control valves GRLA/GRLZ, standard

FESTO

Technical data – Push-in connector QS, metal

Materials

Sectional view



One-way flow control valve



1	Adjusting screw	Slotted head screw: Brass Knurled screw: High-alloy stainless steel
2	Swivel connection	Die-cast zinc
3	Releasing ring	POM
4	Threaded plug	Wrought aluminium alloy GRLA/GRLZ-M5: Brass
–	Seals	NBR
Note on materials		GRLA-...-RS Free of copper and PTFE

Dimensions

Download CAD Data → www.festo.com/us/cad

Slotted head screw

Knurled screw



Type	Connection D	Tubing O.D. D1	B	D2 Ø	D3 Ø	H	H1	Lmax.		L1	L2	=C
								Slotted head screw	Knurled screw			
GRL...-M5	M5	3	8.9	8.2 ±0.15	8.9 ±0.07	22.4	18	21.4	31.3	3.7 +0.17/-0.25	11.65	8
		4	9.9	10.0 ±0.2		24.7	20.3				10.65	
		6	12	12.0 ±0.2		26.5	22				10.65	
GRL...-1/8	G1/8	3	13.8	10.2 ±0.2	13.8 ±0.07	31.9	25	26.9	40.4	5.1 +0.17/-0.25	14.4	12
		4		10.2 ±0.2		29.4	22.5				13.7	
		6		12.5 ±0.2		32.6	25.7				13.7	12
		8		14.5 ±0.2		35.6	28.7				13.7	
GRLA-1/8-...-MF	G1/8	6	13.8	12.5 ±0.2	17.8 ±0.15	36.6	27.7	31.5	–	5.1 +0.17/-0.25	17.2	15
		8		14.5 ±0.2		39.6	30.7				17.2	
GRLA-1/4	G1/4	6	17.8	12.5 ±0.2	17.8 ±0.15	36.6	27.7	31.5	48.3	5.9 +0.17/-0.25	17.2	15
		8		14.5 ±0.2		30.7	30.7				16.1	
		10		17.5 ±0.2		42.0	33.1				16.1	
GRLA-3/8	G3/8	6	22.4	12.5 ±0.2	22.4 ±0.15	39.8	28.6	36.0	55.3	6.95 +0.15/-0.3	20.3	19
		8		14.5 ±0.2		44.1	32.9				19.3	
		10		17.5 ±0.2		46.7	35.5				19.3	
GRLA-1/2	G1/2	12	27.8	20.5 ±0.15	27.8 ±0.15	55.3	41.4	42.3	65.7	8.15 +0.15/-0.3	23.0	24

One-way flow control valves GRLA/GRLZ, standard

FESTO

Technical data – Push-in connector QS, metal

Ordering data – Exhaust air one-way flow control function									
	Pneumatic connection		Standard nominal flow rate q _N at 6 → 5 bar		Standard flow rate q _n at 6 → 0 bar		Weight	Part No.	Type
			in direction of flow control	in non-return direction	in direction of flow control	in non-return direction			
	2	1	[l/min]	[l/min]	[l/min]	[l/min]			
Slotted head screw									
	M5	QS-3	100	60 ... 100	145	150 ... 170	13	193137	GRLA-M5-QS-3-D
		QS-4	110	65 ... 110	165	140 ... 160		193138	GRLA-M5-QS-4-D
		QS-6	115	70 ... 110	185	145 ... 170		193139	GRLA-M5-QS-6-D
	G1/8	QS-3	130	100 ... 130	180	200 ... 220	22	193142	GRLA-1/8-QS-3-D
		QS-4	160	120 ... 190	250	270 ... 300		193143	GRLA-1/8-QS-4-D
		QS-6	185	160 ... 240	370	330 ... 390		193144	GRLA-1/8-QS-6-D
			400	290 ... 420	600	570 ... 680	32	537075	GRLA-1/8-QS-6-MF-D
		QS-8	215	175 ... 250	400	330 ... 410	22	193145	GRLA-1/8-QS-8-D
			475	325 ... 500	720	610 ... 760	32	537076	GRLA-1/8-QS-8-MF-D
	G1/4	QS-6	400	290 ... 420	600	570 ... 680	42	193146	GRLA-1/4-QS-6-D
		QS-8	475	325 ... 500	720	610 ... 760		193147	GRLA-1/4-QS-8-D
		QS-10	480	345 ... 500	760	630 ... 790		193148	GRLA-1/4-QS-10-D
	G3/8	QS-6	495	320 ... 495	740	840 ... 890	60	193149	GRLA-3/8-QS-6-D
		QS-8	820	450 ... 850	1,300	1,080 ... 1,420		193150	GRLA-3/8-QS-8-D
		QS-10	900	540 ... 975	1,400	1,160 ... 1,620		193151	GRLA-3/8-QS-10-D
	G1/2	QS-12	1,580	925 ... 1,605	2,220	1,910 ... 2,500	106	193152	GRLA-1/2-QS-12-D
Knurled screw									
	M5	QS-3	100	60 ... 100	145	150 ... 170	14	197576	GRLA-M5-QS-3-RS-D
		QS-4	110	65 ... 110	165	140 ... 160		197577	GRLA-M5-QS-4-RS-D
		QS-6	115	70 ... 110	185	145 ... 170		197578	GRLA-M5-QS-6-RS-D
	G1/8	QS-3	130	100 ... 130	180	200 ... 220	23	197579	GRLA-1/8-QS-3-RS-D
		QS-4	160	120 ... 190	250	270 ... 300		197580	GRLA-1/8-QS-4-RS-D
		QS-6	185	160 ... 240	370	330 ... 390		197581	GRLA-1/8-QS-6-RS-D
		QS-8	215	175 ... 250	400	330 ... 410	24	534337	GRLA-1/8-QS-8-RS-D
	G1/4	QS-6	400	290 ... 420	600	570 ... 680	50	534338	GRLA-1/4-QS-6-RS-D
		QS-8	475	325 ... 500	720	610 ... 760		534339	GRLA-1/4-QS-8-RS-D
		QS-10	480	345 ... 500	760	630 ... 790		534340	GRLA-1/4-QS-10-RS-D
	G3/8	QS-6	495	320 ... 495	740	840 ... 890	72	534341	GRLA-3/8-QS-6-RS-D
		QS-8	820	450 ... 850	1,300	1,080 ... 1,420		534342	GRLA-3/8-QS-8-RS-D
		QS-10	900	540 ... 975	1,400	1,160 ... 1,620		534343	GRLA-3/8-QS-10-RS-D
	G1/2	QS-12	1,580	925 ... 1,605	2,220	1,910 ... 2,500	124	534344	GRLA-3/8-QS-12-RS-D

Ordering data – Supply air one-way flow control function									
	Pneumatic connection		Standard nominal flow rate q _N N at 6 → 5 bar		Standard flow rate q _n at 6 → 0 bar		Weight	Part No.	Type
			in direction of flow control	in non-return direction	in direction of flow control	in non-return direction			
	2	1	[l/min]	[l/min]	[l/min]	[l/min]			
Slotted head screw									
	M5	QS-3	100	60 ... 100	135	130 ... 160	13	193153	GRLZ-M5-QS-3-D
		QS-4	110	65 ... 110	160	150 ... 180		193154	GRLZ-M5-QS-4-D
		QS-6	115	70 ... 110	170	160 ... 200		193155	GRLZ-M5-QS-6-D
	G1/8	QS-3	130	100 ... 130	200	180 ... 200	22	193156	GRLZ-1/8-QS-3-D
		QS-4	160	120 ... 190	300	260 ... 290		193157	GRLZ-1/8-QS-4-D
		QS-6	185	160 ... 240	340	390 ... 460		193158	GRLZ-1/8-QS-6-D
		QS-8	215	175 ... 250	370	390 ... 470		193159	GRLZ-1/8-QS-8-D

One-way flow control valves GRLA/GRLZ, standard



FESTO

Technical data – Female thread/barbed connector, metal

One-way flow control function

Exhaust air

Supply air



Flow rate


83 ... 4,320 l/min

Temperature range

–10 ... +60 °C

Pressure

0.2 ... 10 bar



GRLA/GRLZ

GRLA/GRLZ-...-RS

GRLA/GRLZ-...-PK

General technical data – GRLA									
Valve function	Exhaust air one-way flow control function								
Connection type	Female thread						Barbed connector		
Pneumatic connection 2	M5	G $\frac{1}{8}$	G $\frac{1}{4}$	G $\frac{3}{8}$	G $\frac{1}{2}$	G $\frac{3}{4}$	M5	G $\frac{1}{8}$	G $\frac{1}{4}$
Pneumatic connection 1	M5 ¹⁾	G $\frac{1}{8}$ ¹⁾	G $\frac{1}{4}$ ¹⁾	G $\frac{3}{8}$ ¹⁾	G $\frac{1}{2}$ ¹⁾	G $\frac{3}{4}$ ¹⁾	PK-3, PK-4	PK-3, PK-4, PK-6	PK-4, PK-6
Adjustment component	Slotted head screw								
	Knurled screw –								
Type of mounting	Screw-in								
Mounting position	Any								
Max. tightening torque [Nm]	1.5	6	11	20	40	60	1.5	6	11

1) – Note: This product conforms to ISO 1179-1 and ISO 228-1.

General technical data – GRLZ						
Valve function	Supply air one-way flow control function					
Connection type	Female thread			Barbed connector		
Pneumatic connection 2	M5	G $\frac{1}{8}$	G $\frac{1}{4}$	M5	G $\frac{1}{8}$	G $\frac{1}{4}$
Pneumatic connection 1	M5 ¹⁾	G $\frac{1}{8}$ ¹⁾	G $\frac{1}{4}$ ¹⁾	PK-3, PK-4	PK-3, PK-4, PK-6	PK-4, PK-6
Adjustment component	Slotted head screw					
	Knurled screw –					
Type of mounting	Screw-in					
Mounting position	Any					
Max. tightening torque [Nm]	1.5	6	11	1.5	6	11

1) – Note: This product conforms to ISO 1179-1 and ISO 228-1.

Operating and environmental conditions						
Pneumatic connection 2	M5	G $\frac{1}{8}$	G $\frac{1}{4}$	G $\frac{3}{8}$	G $\frac{1}{2}$	G $\frac{3}{4}$
Operating pressure [bar]	0.2 ... 10	0.3 ... 10				
Operating medium	Filtered compressed air, lubricated or unlubricated, grade of filtration 40µm					
Ambient temperature [°C]	–10 ... +60					
Temperature of medium [°C]	–10 ... +60					
Storage temperature [°C]	–10 ... +40					
Certification	GRLA: Germanischer Lloyd					


One-way flow control valves GRLA/GRLZ, standard

FESTO

Technical data – Female thread/barbed connector, metal


Standard nominal flow rate q_{nN} at 6 $\rightarrow$ 5 bar
as a function of turns of the adjusting screw n

GRLA/GRLZ-M5




Standard flow rate q_n at 6 $\rightarrow$ 0 bar
as a function of turns of the adjusting screw n


GRLA/GRLZ-M5




GRLA/GRLZ-1/8




GRLA/GRLZ-1/8



GRLA/GRLZ-1/4



GRLA/GRLZ-1/4




One-way flow control valves GRLA/GRLZ, standard

FESTO

Technical data – Female thread/barbed connector, metal


Standard nominal flow rate q_{nN} at 6 $\rightarrow$ 5 bar
as a function of turns of the adjusting screw n

GRLA- $\frac{3}{8}$




Standard flow rate q_n at 6 $\rightarrow$ 0 bar
as a function of turns of the adjusting screw n


GRLA- $\frac{3}{8}$




GRLA- $\frac{1}{2}$




GRLA- $\frac{1}{2}$



GRLA- $\frac{3}{4}$




GRLA- $\frac{3}{4}$



Materials

Sectional view



One-way flow control valve

1	Adjusting screw	Brass, GRLA-...-CT: Aluminium
2	Swivel connection	Die-cast zinc
3	Threaded plug	Wrought aluminium alloy GRLA/GRLZ-M5: Nickel-plated brass
–	Seals	NBR
Note on materials		GRLA-...-CT: Free of copper and PTFE GRLA- $\frac{1}{2}$ -B: RoHS-compliant

One-way flow control valves GRLA/GRLZ, standard

FESTO



Technical data – Female thread/barbed connector, metal

Dimensions – Female thread connection type

Download CAD Data → www.festo.com/us/cad

Slotted head screw

Knurled screw



Type	Connection D	B	H	H1	Lmax.		L1	L2	⌀
					Slotted head screw	Knurled screw			
GRL...-M5	M5	10 -0.15	17.5	12.5	17.6	27.3	4.0 ±0.3	7.1	9
GRL...-1/8	G1/8	16 -0.15	28	20	25.2	38.6	5.3 +0.45/-0.35	10.3	14
GRL...-1/4	G1/4	20 -0.2	36	26	30.8	54.8	8.2 +0.45/-0.35	13.2	17
GRLA-3/8	G3/8	25 -0.2	41	28.5	37.2	—	8.8 +0.45/-0.35	15.5	22
GRLA-1/2	G1/2	32 -0.2	53	37	48.6	—	12.8 ±0.45	18.9	27
GRLA-3/4	G3/4	41 -0.3	64	43.5	60.2	—	13.5 ±0.5	24.5	36

Note: This product conforms to ISO 1179-1 and ISO 228-1



Dimensions – Barbed connector connection type

Download CAD Data → www.festo.com/us/cad

Slotted head screw

GRL...-M5

GRL...-1/8/GRL...-1/4



3 Barbed connector

4 Union nut

Type	Connection D	B	H	H1	L max.	L1	L2	⌀
GRL...-M5-PK-3	M5	10 -0.15	19.7	14.7	17.6	4.0 ±0.3	8.5	9
GRL...-M5-PK-4		10 -0.15	21.7	16.7	17.6	4.0 ±0.3	8.5	9
GRL...-1/8-PK-3	G1/8	16 -0.15	27.1	19.1	25.2	5.3 +0.45/-0.35	13.4	14
GRL...-1/8-PK-4		16 -0.15	30.2	22.2	25.2	5.3 +0.45/-0.35	13.4	14
GRL...-1/8-PK-6		16 -0.15	30.3	22.3	25.2	5.3 +0.45/-0.35	12.0	14
GRL...-1/4-PK-4	G1/4	20 -0.2	34.2	24.2	30.8	8.2 +0.45/-0.35	16.9	17
GRL...-1/4-PK-6		20 -0.2	34.3	24.3	30.8	8.2 +0.45/-0.35	17.2	17

One-way flow control valves GRLA/GRLZ, standard

FESTO

Technical data – Female thread/barbed connector, metal

Ordering data – Exhaust air one-way flow control function									
	Pneumatic connection		Standard nominal flow rate q _N N at 6 → 5 bar		Standard flow rate q _n at 6 → 0 bar		Weight	Part No.	Type
			in direction of flow control	in non-return direction	in direction of flow control	in non-return direction			
	2	1	[l/min]	[l/min]	[l/min]	[l/min]			
Slotted head screw									
	M5	M5	95	76 ... 95	169	135 ... 170	11	151160	GRLA-M5-B
	G1/8	G1/8	340	260 ... 420	615	470 ... 760	28	151165	GRLA-1/8-B
	G1/4	G1/4	610	450 ... 820	1,200	885 ... 1,615	59	151172	GRLA-1/4-B
	G3/8	G3/8	1,450	970 ... 1,600	2,300	1,540 ... 2,540	97	151178	GRLA-3/8-B
	G1/2	G1/2	2,100	1,550 ... 2,200	4,000	2,950 ... 4,190	204	151179	GRLA-1/2-B
	G3/4	G3/4	4,320	3,220 ... 4,720	7,300	5,440 ... 7,300	377	151180	GRLA-3/4-B
	M5	PK-3	83	72 ... 83	140	120 ... 140	10	151161	GRLA-M5-PK-3-B
		PK-4	83	76 ... 88	140	128 ... 148	10	151162	GRLA-M5-PK-4-B
	G1/8	PK-3 ¹⁾	110	100 ... 110	162	145 ... 165	22	151166	GRLA-1/8-PK-3-B
		PK-4 ¹⁾	230	190 ... 240	360	295 ... 375	25	151167	GRLA-1/8-PK-4-B
		PK-6 ¹⁾	300	210 ... 290	455	320 ... 440	26	151168	GRLA-1/8-PK-6-B
	G1/4	PK-4 ¹⁾	260	220 ... 260	370	315 ... 370	44	151173	GRLA-1/4-PK-4-B
		PK-6 ¹⁾	540	410 ... 585	840	635 ... 910	45	151174	GRLA-1/4-PK-6-B
Knurled screw									
	M5	M5	95	76 ... 95	169	135 ... 170	12	151163	GRLA-M5-RS-B
	G1/8	G1/8	340	260 ... 420	615	470 ... 760	30	151169	GRLA-1/8-RS-B
	G1/4	G1/4	610	450 ... 820	1,200	885 ... 1,615	59	151175	GRLA-1/4-RS-B

1) Via union nut

Ordering data – Supply air one-way flow control function									
	Pneumatic connection		Standard nominal flow rate q _{nN} at 6 → 5 bar		Standard flow rate q _n at 6 → 0 bar		Weight	Part No.	Type
			in direction of flow control	in non-return direction	in direction of flow control	in non-return direction			
	2	1	[l/min]	[l/min]	[l/min]	[l/min]			
Slotted head screw									
	M5	M5	95	76 ... 95	169	135 ... 170	11	151183	GRLZ-M5-B
	G ¹ / ₈	G ¹ / ₈	340	260 ... 420	615	470 ... 760	28	151188	GRLZ- ¹ / ₈ -B
	G ¹ / ₄	G ¹ / ₄	610	450 ... 820	1,200	885 ... 1,615	59	151195	GRLZ- ¹ / ₄ -B
	M5	PK-3	83	72 ... 83	140	120 ... 140	10	151184	GRLZ-M5-PK-3-B
		PK-4	83	76 ... 88	140	125 ... 150	10	151185	GRLZ-M5-PK-4-B
	G ¹ / ₈	PK-3 ¹⁾	110	100 ... 110	162	145 ... 165	22	151189	GRLZ- ¹ / ₈ -PK-3-B
		PK-4 ¹⁾	230	190 ... 240	360	295 ... 375	25	151190	GRLZ- ¹ / ₈ -PK-4-B
		PK-6 ¹⁾	300	210 ... 290	455	320 ... 440	26	151191	GRLZ- ¹ / ₈ -PK-6-B
	G ¹ / ₄	PK-4 ¹⁾	260	220 ... 260	370	315 ... 370	44	151196	GRLZ- ¹ / ₄ -PK-4-B
		PK-6 ¹⁾	540	410 ... 585	840	635 ... 910	45	151197	GRLZ- ¹ / ₄ -PK-6-B
Knurled screw									
	M5	M5	95	76 ... 95	169	135 ... 170	12	151186	GRLZ-M5-RS-B
	G ¹ / ₈	G ¹ / ₈	340	260 ... 420	615	470 ... 760	30	151192	GRLZ- ¹ / ₈ -RS-B
	G ¹ / ₄	G ¹ / ₄	610	450 ... 820	1,200	885 ... 1,615	59	151198	GRLZ- ¹ / ₄ -RS-B


1) Via union nut

One-way flow control valves GRLSA, standard

Technical data – Push-in connector QS, metal

One-way flow control function

Exhaust air



Flow rate

0 ... 450 l/min

Temperature range

–10 ... +60 °C


Pressure

0.2 ... 10 bar




This one-way flow control valve offers the ideal conditions for optimum and easy setting of the flow rate in a unique design.

There are two setting options:



1 Gradual for preselection of the flow range in 5 stages via rotary switch: A, B, C, D, E



2 Infinitely variable for precision adjustment using internal hex via a scale marked from 0 to 10



General technical data		
Valve function	Exhaust air one-way flow control function	
Pneumatic connection 2	G1/8	G1/4
Pneumatic connection 1	QS-6	QS-8
Adjustment component	Rotary knob with scale and internal hex	
Actuation type	Manual	
Type of mounting	Screw-in	
Mounting position	Any	
Max. tightening torque [Nm]	5.5	11

Operating and environmental conditions		
Operating pressure [bar]	0.2 ... 10	
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)	
Ambient temperature [°C]	–10 ... +60	
Temperature of medium [°C]	–10 ... +60	
Storage temperature [°C]	–10 ... +40	


One-way flow control valves GRLSA, standard

Technical data – Push-in connector QS, metal

FESTO


Standard nominal flow rate q_{nN} at 6 $\rightarrow$ 5 bar
as a function of the position of the flow control screw (scale) n

GRLSA-1/8




Standard flow rate q_n at 6 $\rightarrow$ 0 bar
as a function of the position of the flow control screw (scale) n


GRLSA-1/8



GRLSA-1/4



GRLSA-1/4




- Stage: A
- - - Stage: B
- Stage: C
- - - Stage: D
- · - Stage: E

Flow rate value tolerance: $\pm 20\%$

Materials

Sectional view



One-way flow control valve

1	Adjusting screw	PA, reinforced
2	Swivel connection	Die-cast zinc
3	Releasing ring	POM
5	Hollow bolt	Anodised wrought aluminium alloy
-	Seals	NBR
Note on materials		Free of copper and PTFE


One-way flow control valves GRLSA, standard

Technical data – Push-in connector QS, metal

Dimensions

Download CAD Data → www.festo.com/us/cad

Rotary knob with scale and internal hex



Type	Connection	Tubing O.D.	B	B1	B2	H	L max.	L1	L2	L3	≈C1	≈C2
	D	D1										
GRLSA-1/8	G1/8	6	12.5	13.8	15	25.7	36.6	5.1	13.5	2	12	3
GRLSA-1/4	G1/4	8	14.5	17.8	18.8	30.75	46.5	7	17.2	3	15	3

Ordering data – Exhaust air one-way flow control function

	Pneumatic connection		Standard nominal flow rate qnN at 6 → 5 bar		Standard flow rate qn at 6 → 0 bar		Weight	Part No.	Type
			in direction of flow control	in non-return direction	in direction of flow control	in non-return direction			
	2	1	[l/min]	[l/min]	[l/min]	[l/min]			
Rotary knob with scale and internal hex									
	G1/8	QS-6	0 ... 250	180 ... 310	0 ... 410	430 ... 540	19.5	540661	GRLSA-1/8-QS-6
	G1/4	QS-8	0 ... 450	390 ... 570	0 ... 700	820 ... 930	34.8	540662	GRLSA-1/4-QS-8


One-way flow control valves VFOC, standard

Technical data – Push-in connector QS, metal

FESTO

One-way flow control function

Supply air



Flow rate

0 ... 270 l/min

Temperature range

-10 ... +60 °C

Pressure


0.2 ... 10 bar




General technical data		
Valve function	Supply air one-way flow control function	
Pneumatic connection 2	Push-in sleeve QS-4	Push-in sleeve QS-6
Pneumatic connection 1	QS-4	QS-6
Note on the pneumatic connection 2	Only suitable for push-in connector QS from Festo	
Adjustment component	Slotted head screw	
Actuation type	Manual	
Type of mounting	Plug-in, with push-in sleeve	
Mounting position	Any	

Operating and environmental conditions		
Operating pressure	[bar]	0.2 ... 10
Operating medium	Dried air, lubricated or unlubricated	
Ambient temperature	[°C]	-10 ... +60
Temperature of medium	[°C]	-10 ... +60
Storage temperature	[°C]	-10 ... +40

Standard nominal flow rate q_{nN} at 6 → 5 bar
as a function of turns of the adjusting screw n



Standard flow rate q_n at 6 → 0 bar
as a function of turns of the adjusting screw n




One-way flow control valves VFOC, standard

Technical data – Push-in connector QS, metal

FESTO

Materials

Sectional view




One-way flow control valve

1	Adjusting screw	High-alloy stainless steel
2	Swivel connection	Die-cast zinc
3	Releasing ring	POM
4	Hollow bolt	Black anodised wrought aluminium alloy
–	Seals	NBR
Note on materials		Free of copper and PTFE

Dimensions

Download CAD Data → www.festo.com/us/cad

Slotted head screw



Note

The push-in sleeves of the one-way flow control valves VFOC are exclusively matched to push-in fittings QS from Festo

→ www.festo.com/catalogue.
This combination alone guarantees a secure grip in the push-in fitting.

Type	Push-in sleeve Ø D	Tubing O.D. D1	D2 Ø	D3 Ø	H	H1	L	L1	L2
VFOC-S-S4-Q4	4	4	10	8.9	24.7	20.3	23.2	14.8	13.2
VFOC-S-S6-Q6	6	6	12.5	13.8	32.6	25.7	28	16.5	15.8

Ordering data – Supply air one-way flow control function

	Pneumatic connection		Standard nominal flow rate q _N at 6 → 5 bar		Standard flow rate q _n at 6 → 0 bar		Weight	Part No.	Type
			in direction of flow control	in non-return direction	in direction of flow control	in non-return direction			
	2	1	[l/min]	[l/min]	[l/min]	[l/min]			
Slotted head screw									
	Push-in sleeve QS-4	QS-4	0 ... 100	60 ... 100	0 ... 170	130 ... 160	9.2	559723	VFOC-S-S4-Q4
	Push-in sleeve QS-6	QS-6	0 ... 270	170 ... 260	0 ... 430	330 ... 400	21.6	559724	VFOC-S-S6-Q6


One-way flow control valves GRLA-F, standard

Technical data – Push-in connector QS, chromed metal

FESTO

One-way flow control function

Exhaust air



Flow rate

100 ... 530 l/min

Temperature range

0 ... +150 °C

Pressure

0.2 ... 10 bar

- Can be swivelled 360° around the screw-in axis after mounting



General technical data		
Valve function	Exhaust air one-way flow control function	
Pneumatic connection 2	G1/8	G1/4
Pneumatic connection 1	QS-4, QS-6, QS-8	QS-6, QS-8
Adjustment component	Slotted head screw	
Actuation type	Manual	
Type of mounting	Screw-in	
Mounting position	Any	
Max. tightening torque [Nm]	5.5	11


Operating and environmental conditions		
Operating pressure [bar]	0.2 ... 10	
Operating medium	Filtered compressed air, lubricated or unlubricated, grade of filtration 40 µm	
Ambient temperature [°C]	0 ... +150	
Temperature of medium [°C]	0 ... +150	
Storage temperature [°C]	-10 ... +150	
Corrosion resistance class CRC ¹⁾	3	

1) Corrosion resistance class 3 according to Festo standard 940 070


Components subject to high corrosion stress. External visible parts in direct contact with industrial atmospheres or media such as solvents and cleaning agents, with a predominantly functional requirement for the surface.

Standard nominal flow rate q_{nN} at 6 → 5 bar as a function of turns of the adjusting screw n

GRLA-F-1/8



GRLA-F-1/4




One-way flow control valves GRLA-F, standard

Technical data – Push-in connector QS, chromed metal

FESTO

Materials

Sectional view




One-way flow control valve

1	Adjusting screw	High-alloy stainless steel
2	Swivel connection	Nickel and chrome-plated brass
3	Releasing ring	Nickel and chrome-plated brass
4	Hollow bolt	Wrought aluminium alloy
-	Seals	FPM
Note on materials		Free of copper and PTFE

Dimensions

Download CAD Data → www.festo.com/us/cad

Slotted head screw



Type	Connection	Tubing O.D.	B	D2 Ø	H	H1	L max.	L1	≙
	D	D1							
GRLA-F-1/8	G1/8	4	13.8	9	28.0	21.1	31.6	5.2	12
		6		11	31.0	24.1			
		8		13	31.9	25.0			
GRLA-F-1/4	G1/4	6	17.8	11	35.1	26.2	34.9	5.9	15
		8		13	35.9	27.0			

Ordering data – Exhaust air one-way flow control function

Pneumatic connection		Standard nominal flow rate qnN at 6 → 5 bar		Standard flow rate qn at 6 → 0 bar		Weight [g]	Part No.	Type	
		in direction of flow control	in non-return direction	in direction of flow control	in non-return direction				
		2	1	[l/min]	[l/min]				[l/min]
Slotted head screw									
	G1/8	QS-4	180	103 ... 188	250	270 ... 300	25	195597	GRLA-F-1/8-QS-4-D
		QS-6	255	111 ... 280	370	330 ... 390		195598	GRLA-F-1/8-QS-6-D
		QS-8	275	132 ... 307	400	330 ... 410		195599	GRLA-F-1/8-QS-8-D
	G1/4	QS-6	430	384 ... 478	600	570 ... 680	37	195600	GRLA-F-1/4-QS-6-D
		QS-8	530	402 ... 578	720	610 ... 760		195601	GRLA-F-1/4-QS-8-D


One-way flow control valves GRLA, standard

Technical data – Push-in connector QS, polymer

FESTO

One-way flow control function

Exhaust air



Flow rate

520 ... 650 l/min

Temperature range

-10 ... +60 °C

Pressure

0.2 ... 10 bar

- Can be swivelled 360° around the screw-in axis after mounting




General technical data			
Valve function		Exhaust air one-way flow control function	
Pneumatic connection 2		G $\frac{1}{8}$	G $\frac{1}{4}$ G $\frac{3}{8}$
Pneumatic connection 1		QS-6, QS-8	QS-6, QS-8 QS-6, QS-8
Adjustment component	Knurled screw		
Actuation type	Manual		
Type of mounting	Screw-in		
Mounting position	Any		
Max. tightening torque [Nm]	4	11	40
Perm. actuation torque for regulating screw [Nm]	0.4		

Operating and environmental conditions	
Operating pressure [bar]	0.2 ... 10
Operating medium	Filtered compressed air, lubricated or unlubricated, grade of filtration 40 µm
Ambient temperature [°C]	-10 ... +60
Temperature of medium [°C]	-10 ... +60
Storage temperature [°C]	-10 ... +40
Corrosion resistance class CRC ¹⁾	2


1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Standard nominal flow rate q_{nN} at 6 → 5 bar
as a function of turns of the adjusting screw n



Standard flow rate q_n at 6 → 0 bar
as a function of turns of the adjusting screw n




One-way flow control valves GRLA, standard

Technical data – Push-in connector QS, polymer

FESTO

Materials

Sectional view




One-way flow control valve

1	Adjusting screw	Brass
2	Knurled head	Wrought aluminium alloy
3	Swivel connection	PBT, reinforced
4	Releasing ring	POM
5	Threaded plug	Wrought aluminium alloy
– Seals		TPE-U(PU) NBR
Note on materials		Free of copper and PTFE RoHS-compliant

Dimensions


Download CAD Data → www.festo.com/us/cad

Knurled screw



Type	Connection	Tubing O.D.	D2 Ø	D3	H1	L max.	L1	L2	⌀
	D	D1							
GRLA-1/8	G1/8	6	13.0 ±0.25	17.9 -0.1	27.2	52.8	4.9	22.6	13
		8	16.8 ±0.4		35.4				
GRLA-1/4	G1/4	6	13.0 ±0.25	17.9 -0.1	27.2	53.6	5.8	22.3	17
		8	16.8 ±0.4		35.4				
GRLA-3/8	G3/8	6	13.0 ±0.25	17.9 -0.1	27.2	53.8	6.8	22.3	19
		8	16.8 ±0.4		35.4				

Ordering data – Exhaust air one-way flow control function

Pneumatic connection		Standard nominal flow rate qnN at 6 → 5 bar		Standard flow rate qn at 6 → 0 bar		Weight [g]	Part No.	Type	
		in direction of flow control	in non-return direction	in direction of flow control	in non-return direction				
		2	1	[l/min]	[l/min]				[l/min]
Knurled screw									
	G1/8	QS-6	520	400 ... 550	720	600 ... 750	25	162965	GRLA-1/8-QS-6-RS-B
		QS-8	650	600 ... 750	1,080	800 ... 1,250		162966	GRLA-1/8-QS-8-RS-B
	G1/4	QS-6	520	400 ... 550	720	600 ... 750	30	162967	GRLA-1/4-QS-6-RS-B
		QS-8	650	600 ... 750	1,130	800 ... 1,250		162968	GRLA-1/4-QS-8-RS-B
	G3/8	QS-6	530	400 ... 550	720	600 ... 750	40	162969	GRLA-3/8-QS-6-RS-B
		QS-8	650	600 ... 750	1,130	900 ... 1,250		162970	GRLA-3/8-QS-8-RS-B

One-way flow control valves GRLA/GRLZ/GRGA/GRGZ, mini



FESTO

Technical data – Push-in connector QS, metal

One-way flow control function

Exhaust air

Supply air



Flow rate

40 ... 48 l/min


Temperature range

–10 ... +60 °C

Pressure

0.2 ... 10 bar

- Low flow: precision adjustment for low speed



General technical data – GRLA/GRGA		
Valve function	Exhaust air one-way flow control function	
Pneumatic connection 2	M3	M5
Pneumatic connection 1	QS-3	QS-3, QS-4
Adjustment component	Slotted head screw	
Type of mounting	Screw-in	
Mounting position	Any	
Max. tightening torque [Nm]	0.3	1.5

General technical data – GRLZ/GRGZ		
Valve function	Supply air one-way flow control function	
Pneumatic connection 2	M3	M5
Pneumatic connection 1	QS-3	QS-3, QS-4
Adjustment component	Slotted head screw	
Type of mounting	Screw-in	
Mounting position	Any	
Max. tightening torque [Nm]	0.3	1.5

Operating and environmental conditions		
Operating pressure [bar]	0.2 ... 10	
Operating medium	Filtered compressed air, lubricated or unlubricated, grade of filtration 40 µm	
Ambient temperature [°C]	–10 ... +60	
Temperature of medium [°C]	–10 ... +60	
Storage temperature [°C]	–10 ... +40	
Certification	GRLA: Germanischer Lloyd	


One-way flow control valves GRLA/GRLZ/GRGA/GRGZ, mini

FESTO

Technical data – Push-in connector QS, metal


Standard nominal flow rate q_{nN} at 6 $\rightarrow$ 5 bar
as a function of turns of the adjusting screw n

GRLA/GRLZ/GRGA/GRGZ-M3




Standard flow rate q_n at 6 $\rightarrow$ 0 bar
as a function of turns of the adjusting screw n


GRLA/GRLZ/GRGA/GRGZ-M3



GRLA/GRLZ-M5




GRLA/GRLZ-M5



Materials

Sectional view





One-way flow control valve

1	Adjusting screw	Brass
2	Swivel connection	Die-cast zinc
3	Releasing ring	POM
4	Threaded plug	Nickel-plated brass
–	Seals	NBR

One-way flow control valves GRLA/GRLZ/GRGA/GRGZ, mini

FESTO

Technical data – Push-in connector QS, metal

Dimensions						Download CAD Data → www.festo.com/us/cad					
GRLA/GRLZ, elbow outlet						GRGA/GRGZ, parallel outlet					
											

Type	Connection	Tubing O.D.	B	H	H1	H2	L max.	L1	L2	L3	⌀
GRLA/GRLZ	M3	3	8 -0.15	20	15.8	-	16.6	2.3 +0.15/-0.3	7	-	7
	M5	3	9.8 -0.15	22.4	18.4		17.7	3.1 +0.15/-0.35	7.3		
		4	9.8 -0.15	22.2	18.2		17.7	3.1 +0.15/-0.35	7.3		
GRGA/GRGZ	M3	3	8 -0.15	18	14	9.25	16.6	2.3 +0.15/-0.3	7.5	22	7

Ordering data – Exhaust air one-way flow control function										
	Pneumatic connection		Standard nominal flow rate qnN at 6 → 5 bar		Standard flow rate qn at 6 → 0 bar		Weight	Part No.	Type	
			in direction of flow control	in non-return direction	in direction of flow control	in non-return direction				
	2	1	[l/min]	[l/min]	[l/min]	[l/min]				[g]
Slotted head screw										
	M3	QS-3	41	27 ... 50	95	75 ... 110	7	175041	GRLA-M3-QS-3	
	M5	QS-3	40	46 ... 70	80	90 ... 140	9	175053	GRLA-M5-QS-3-LF-C	
		QS-4	40	50 ... 75	80	100 ... 150	9	175056	GRLA-M5-QS-4-LF-C	
	M3	QS-3	41	27 ... 50	95	75 ... 110	14	175044	GRGA-M3-QS-3	

Ordering data – Supply air one-way flow control function										
	Pneumatic connection		Standard nominal flow rate qnN at 6 → 5 bar		Standard flow rate qn at 6 → 0 bar		Weight	Part No.	Type	
			in direction of flow control	in non-return direction	in direction of flow control	in non-return direction				
	2	1	[l/min]	[l/min]	[l/min]	[l/min]				[g]
Slotted head screw										
	M3	QS-3	41	27 ... 44	95	75 ... 100	7	175043	GRLZ-M3-QS-3	
	M5	QS-3	48	36 ... 52	80	60 ... 90	9	175055	GRLZ-M5-QS-3-LF-C	
		QS-4	48	40 ... 65	80	65 ... 110	9	175058	GRLZ-M5-QS-4-LF-C	
	M3	QS-3	41	27 ... 44	95	75 ... 100	14	175046	GRGZ-M3-QS-3	

One-way flow control valves GRLA/GRLZ, mini



FESTO

Technical data – Female thread, metal

One-way flow control function

Exhaust air

Supply air



Flow rate

0 ... 18 l/min

Temperature range

–10 ... +60 °C

Pressure

0.2 ... 10 bar




General technical data – GRLA	
Valve function	Exhaust air one-way flow control function
Pneumatic connection 2	M3
Pneumatic connection 1	M3
Adjustment component	Slotted head screw
Type of mounting	Screw-in
Mounting position	Any
Max. tightening torque [Nm]	0.3


General technical data – GRLZ	
Valve function	Supply air one-way flow control function
Pneumatic connection 2	M3
Pneumatic connection 1	M3
Adjustment component	Slotted head screw
Type of mounting	Screw-in
Mounting position	Any
Max. tightening torque [Nm]	0.3

Operating and environmental conditions	
Operating pressure [bar]	0.2 ... 10
Operating medium	Filtered compressed air, lubricated or unlubricated, grade of filtration 40 µm
Ambient temperature [°C]	–10 ... +60
Temperature of medium [°C]	–10 ... +60
Storage temperature [°C]	–10 ... +40
Certification	GRLA: Germanischer Lloyd

Standard nominal flow rate q_{nN} at 6 → 5 bar
as a function of turns of the adjusting screw n



Standard flow rate q_n at 6 → 0 bar
as a function of turns of the adjusting screw n




One-way flow control valves GRLA/GRLZ, mini

Technical data – Female thread, metal

FESTO

Materials

Sectional view




One-way flow control valve

1	Adjusting screw	Brass
2	Swivel connection	Die-cast zinc
3	Threaded plug	Nickel-plated brass
–	Seals	NBR

Dimensions

Download CAD Data → www.festo.com/us/cad

Slotted head screw



Type	Connection	B	H	H1	L max.	L1	L2	⌀
GRLA/GRLZ	M3	5 -0.1	9	6.5	13.3	2.5 +0.15/-0.3	6.4	4.5

Ordering data – Exhaust air one-way flow control function

	Pneumatic connection	Standard nominal flow rate q _N at 6 → 5 bar	Standard flow rate q _n at 6 → 0 bar	Weight [g]	Part No.	Type
			in direction of flow control	in non-return direction		
	2	1	[l/min]	[l/min]		

Slotted head screw

	M3	M3	18	18 ... 20	33	33 ... 37	2	175038	GRLA-M3
--	----	----	----	-----------	----	-----------	---	---------------	----------------

Ordering data – Supply air one-way flow control function

	Pneumatic connection	Standard nominal flow rate q _N at 6 → 5 bar	Standard flow rate q _n at 6 → 0 bar	Weight [g]	Part No.	Type
			in direction of flow control	in non-return direction		
	2	1	[l/min]	[l/min]		

Slotted head screw

	M3	M3	18	18 ... 20	33	33 ... 37	2	175040	GRLZ-M3
--	----	----	----	-----------	----	-----------	---	---------------	----------------


One-way flow control valves CRGRLA, corrosion-resistant

FESTO

Technical data – Female thread, stainless steel

One-way flow control function

Exhaust air



Flow rate

95 ... 2,100 l/min

Temperature range

–20 ... +80 °C

Pressure

0.2 ... 10 bar



General technical data						
Valve function	Exhaust air one-way flow control function					
Pneumatic connection 2	M5	G1/8	G1/4	G3/8	G1/2	
Pneumatic connection 1	M5	G1/8	G1/4	G3/8	G1/2	
Adjustment component	Slotted head screw					
Type of mounting	Screw-in					
Mounting position	Any					
Max. tightening torque [Nm]	1.5	6	11	20	40	

Note: This product conforms to ISO 1179-1 and ISO 228-1


Operating and environmental conditions						
Pneumatic connection 2	M5	G1/8	G1/4	G3/8	G1/2	
Operating pressure [bar]	0.2 ... 10	0.3 ... 10				
Operating medium	Filtered compressed air, lubricated or unlubricated, grade of filtration 40 µm					
Ambient temperature [°C]	–20 ... +80					
Temperature of medium [°C]	–10 ... +60					
Storage temperature [°C]	–10 ... +40					
Corrosion resistance class CRC ¹⁾	3					
Certification	Germanischer Lloyd					

1) Corrosion resistance class 3 according to Festo standard 940 070

Components subject to high corrosion stress. External visible parts in direct contact with industrial atmospheres or media such as solvents and cleaning agents, with a predominantly functional requirement for the surface.


Standard nominal flow rate q_{nN} at 6 → 5 bar as a function of turns of the adjusting screw n

CRGRLA-M5, CRGRLA-1/8



Standard flow rate q_n at 6 → 0 bar as a function of turns of the adjusting screw n

CRGRLA-M5, CRGRLA-1/8




One-way flow control valves CRGRLA, corrosion-resistant

FESTO

Technical data – Female thread, stainless steel


Standard nominal flow rate q_{pN} at 6 $\rightarrow$ 5 bar
as a function of turns of the adjusting screw n

CRGRLA-1/4, CRGRLA-3/8, CRGRLA-1/2




Standard flow rate q_n at 6 $\rightarrow$ 0 bar
as a function of turns of the adjusting screw n

CRGRLA-1/4, CRGRLA-3/8, CRGRLA-1/2



Materials

Sectional view



One-way flow control valve



1	Adjusting screw	High-alloy stainless steel
2	Swivel connection	High-alloy stainless steel
3	Threaded plug	High-alloy stainless steel
-	Seals	NBR, FPM

Dimensions

Download CAD Data www.festo.com/us/cad

CRGRLA-M5

CRGRLA-1/8, CRGRLA-1/4, CRGRLA-3/8, CRGRLA-1/2



Type	Connection D	B	H	H1	L	L1	L2	L3	$\approx \varnothing$
CRGRLA-M5	M5	10 -0.25	17.5 $\pm$ 0.3	12.5	23.2	4	7.1	2.5	9
CRGRLA-1/8	G1/8	16 -0.4	28 +0.4/-0.3	20	33.7	5.5	10.3	3.5	14
CRGRLA-1/4	G1/4	20 -0.3	36 +0.4/-0.2	26	38.8	6.5	13.2	3.5	17
CRGRLA-3/8	G3/8	25 -0.3	41 +0.4/-0.2	28.5	48.5	7.5	15.4	5	22
CRGRLA-1/2	G1/2	32 -0.4	53 $\pm$ 0.5	37	62.2	9	18.9	7.5	27

Note: This product conforms to ISO 1179-1 and ISO 228-1

One-way flow control valves CRGRLA, corrosion-resistant

FESTO

Technical data – Female thread, stainless steel


Ordering data – Exhaust air one-way flow control function									
	Pneumatic connection		Standard nominal flow rate q _N N at 6 → 5 bar		Standard flow rate q _n at 6 → 0 bar		Weight [g]	Part No.	Type
			in direction of flow control	in non-return direction	in direction of flow control	in non-return direction			
	2	1	[l/min]	[l/min]	[l/min]	[l/min]			
Slotted head screw									
	M5	M5	95	77 ... 95	165	140 ... 150	10.2	161403	CRGRLA-M5-B
	G1/8	G1/8	340	260 ... 420	580	530 ... 590	37.8	161404	CRGRLA-1/8-B
	G1/4	G1/4	610	450 ... 820	1,265	1,030 ... 1,345	71.6	161405	CRGRLA-1/4-B
	G3/8	G3/8	1,450	970 ... 1,600	2,515	2,095 ... 2,665	126.9	161406	CRGRLA-3/8-B
	G1/2	G1/2	2,100	1,550 ... 2,200	4,265	3,550 ... 4,325	262.3	161407	CRGRLA-1/2-B

One-way flow control valves GRXA, function combination

FESTO

Technical data – Push-in connector QS, metal


One-way flow control function
Exhaust air



Flow rate
130 ... 280 l/min
Temperature range
–10 ... +60 °C
Pressure
0.5 ... 10 bar



Function example:



The function combination consists of a one-way flow control valve and a piloted non-return valve. Exhaust air flow control is active as long as a pilot signal from pneumatic connection 21 is applied. If no pilot signal is applied, the valve shuts off the exhaust air. The compressed air flows unthrottled through the non-return valve in the supply air direction.

- Stop function and speed setting in one housing
- Swivel pilot connection 21 perpendicular to screw-in direction
- Additional pilot connection 1 for crossover interconnection, e.g. for stop function with pressure failure
➔ Function example

General technical data			
Valve function		Exhaust air one-way flow control function	
Pneumatic connection 2		G1/8	G1/4
Pneumatic connection 1		QS-4, QS-6	QS-6, QS-8
Pneumatic connection 21/additional pilot connection 1		QS-4	QS-4
Adjustment component		Slotted head screw	
Actuation type		Pneumatic	
Type of mounting		Screw-in, via male thread	
Mounting position		Any	
Switching time	Off	[ms]	44
	On	[ms]	6
Max. tightening torque		[Nm]	5
			12

Operating and environmental conditions		
Operating pressure p1	[bar]	0.5 ... 10
Pilot pressure p21	[bar]	2 ... 10
Operating/pilot medium		Compressed air in accordance with ISO 8573-1:2010 [7:4:4]
Note on operating/pilot medium		Operation with lubricated medium possible (in which case lubricated operation will always be required)
Ambient temperature	[°C]	–10 ... +60
Temperature of medium	[°C]	–10 ... +60
Storage temperature	[°C]	–10 ... +40

Note

Additional measures are required for use in safety-related applications; in Europe, for example, the standards listed under the EC Machinery Directive must be observed.


Without additional measures in accordance with statutory minimum requirements, the product is not suitable for use in safety-related sections of control systems.

One-way flow control valves GRXA, function combination

FESTO


Technical data – Push-in connector QS, metal

Standard nominal flow rate q_{nN} at 6 $\rightarrow$ 5 bar
as a function of turns of the adjusting screw n




— GRXA-HG-1/4-QS-8,
GRXA-HG-1/4-QS-6
- - GRXA-HG-1/8-QS-6
... GRXA-HG-1/8-QS-4

Standard flow rate q_n at 6 $\rightarrow$ 0 bar
as a function of turns of the adjusting screw n




— GRXA-HG-1/4-QS-8
- - GRXA-HG-1/4-QS-6
- . GRXA-HG-1/8-QS-6
... GRXA-HG-1/8-QS-4

Minimum pilot pressure p_{21} as a function of operating pressure p_1



Materials

Sectional view



One-way flow control valve

1	Adjusting screw	Brass
2	Cap	Anodised wrought aluminium alloy
3	Swivel connection	POM
4	Releasing ring	POM
5	Hollow bolt	Anodised wrought aluminium alloy
-	Seals	NBR

One-way flow control valves GRXA, function combination


FESTO

Technical data – Push-in connector QS, metal

Dimensions


Download CAD Data → www.festo.com/us/cad

Slotted head screw



Type	Connection	Tubing O.D.		B	B1	D3 Ø	D4 Ø	D5 Ø	D6 Ø	H	H1	H2	H3	L	L1	L2	L3	≈C 1	≈C 2
		D1	D2																
GRXA-HG-1/8	G1/8	4	4	28	15	14.5	15.9	9	10	41.8	34.5	33.5	15	49.5	4.9	44.6	17.4	13	12
		4	6	31.5	17.3				12.5	41.8		34.5							
GRXA-HG-1/4	G1/4	4	6	36.1	19.5	19	20.6	9	12.5	52.2	42.7	40.5	21	56.3	5.6	51.4	21.1	17	16
		4	8	40.3	21.5				17	58.2		48.7							

Ordering data – Exhaust air one-way flow control function

	Pneumatic connection		Standard nominal flow rate qnN at 6 → 5 bar		Standard flow rate qn at 6 → 0 bar		Weight	Part No.	Type
			in direction of flow control	in non-return direction	in direction of flow control	in non-return direction			
	2	1	[l/min]	[l/min]	[l/min]	[l/min]			
Slotted head screw									
	G1/8	QS-4	130	100 ... 140 100 ... 140 ¹⁾	210	220 ... 250 230 ... 260 ¹⁾	28.2	525667	GRXA-HG-1/8-QS-4
		QS-6	140	120 ... 160 115 ... 165 ¹⁾	280	260 ... 300 270 ... 300 ¹⁾	28.2	525668	GRXA-HG-1/8-QS-6
	G1/4	QS-6	280	180 ... 260 200 ... 270 ¹⁾	430	410 ... 470 430 ... 490 ¹⁾	58.8	525669	GRXA-HG-1/4-QS-6
		QS-8	280	190 ... 260 200 ... 280 ¹⁾	470	440 ... 500 460 ... 520 ¹⁾	58.8	525670	GRXA-HG-1/4-QS-8

1) Unactuated

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com