

Three-point grippers DHDS

FESTO



Three-point grippers DHDS

Key features

FESTO

At a glance

General information

- Resilient and precise T-slot guide of the gripper jaws
- High gripping forces with compact dimensions
- Gripper jaw centring options
- Max. repetition accuracy
- Gripping force retention
- Internal fixed flow control
- Wide range of options for mounting on drive units


- Sensor technology:
 - Adaptable position sensor for the small gripper sizes
 - Integratable proximity sensors for the medium and large gripper sizes

Flexible range of applications


- Can be used as a double-acting and single-acting gripper
- Compression spring for supplementary or retaining gripping forces
- Suitable for external and internal gripping

The technology in detail

Gripper closed



Gripper open



- 1** Gripper jaw
- 2** Reversing lever
- 3** Piston with magnet

Note

Gripper selection
sizing software
→ www.festo.com

Position sensing/force control

With position transmitter SMAT-8M



Infinite position sensing possible

- Analogue output 0 ... 10 V

With proportional pressure regulator VPPM



Infinite adjustment of the gripping force possible

- Setpoint input
 - 0 ... 10 V
 - 4 ... 20 mA

With proximity sensor SMT-8G



Multiple positions can be sensed:


- Open
- Closed
- Workpiece gripped

Three-point grippers DHDS

Key features

Supply ports


At the side



Mounting options


Size 16

Size 32, 50



- 1 Centring pin
- 2 Mounting screws


Mounting options for external gripper fingers




- 1 Mounting screws
- 2 Gripper fingers
- 3 Centring sleeves

Note


These grippers are not designed for the following or similar sample applications:



- Welding spatter



- Machining
- Aggressive media



- Grinding dust

Three-point grippers DHDS



Peripherals overview

FESTO


Peripherals overview

DHDS-16


DHDS-32, 50



System product for handling and assembly technology



Proportional pressure regulator VPPM



Accessories		
Type	Brief description	→ Page/Internet
1 Connecting cable NEBU	For connecting evaluation unit and signal converter	17
2 Evaluation unit SMH-AE1	<ul style="list-style-type: none"> For evaluating signals for position sensor SMH-S1 For size 16 	17
3 Signal converter SVE4	<ul style="list-style-type: none"> For evaluating signals for position sensor SMH-S1 For size 16 	17
4 Position sensor SMH-S1	<ul style="list-style-type: none"> Adaptable and integratable sensor technology, for sensing the piston position For size 16 	17
5 Centring sleeve ZBH	<ul style="list-style-type: none"> For centring the gripper fingers on the gripper jaws The scope of delivery of the gripper includes 6 centring sleeves 	17
6 Push-in fitting QS	For connecting compressed air tubing with standard O.D.	quick star
7 Proximity sensor SMT-8G	<ul style="list-style-type: none"> For sensing the piston position Proximity sensor does not project past the housing at the bottom For size 32, 50 	18
8 Position transmitter SMAT-8M	<ul style="list-style-type: none"> Continuously senses the position of the piston. Has an analogue output with an output signal in proportion to the piston position. For size 32, 50 	18
9 Adapter kit HMSV, HAPG, HAPS, HMVA	Connecting plate between drive and gripper	14
10 Proportional pressure regulator VPPM	For infinite adjustment of the gripping force	vppm

Three-point grippers DHDS

Type codes


		DHDS	—	32	—	A	—	NC
Type								
DHDS	Three-point gripper							
Size								
Position sensing								
A	Via proximity sensor							
Gripping force retention								
NC	Closing							

Three-point grippers DHDS

Technical data

FESTO

Function
Double-acting
DHDS-...-A



-N- Size
16 ... 50 mm
-T- Stroke
2.5 ... 6 mm

Function – Variants
Single-acting or
with gripping force retention ...
... closing DHDS-...-NC



www.festo.com/en/
Spare_parts_service

General technical data			
Size	16	32	50
Design	Lever		
	Forced motion sequence		
Mode of operation	Double-acting		
Gripper function	Three-point		
Gripping force retention	NC	NC	NC
Number of gripper jaws	3		
Max. applied load per external gripper finger ¹⁾ [N]	0.5	1.5	2.5
Stroke per gripper jaw [mm]	2.5	3.9	6
Pneumatic connection	M3	M5	G1/8
Repetition accuracy ²⁾ [mm]	≤ 0.04		
Max. interchangeability [mm]	≤ ±0.2		
Max. operating frequency [Hz]	≤ 4		
Rotational symmetry [mm]	< Ø 0.2		
Position sensing	Via position sensor		Via proximity sensor, position transmitter
Type of mounting	Via female thread and dowel pin		
Mounting position	Any		

- 1) Valid for unthrottled operation
2) End-position drift under constant conditions of use with 100 consecutive strokes, concentric to the central shaft

Operating and environmental conditions		
Min. operating pressure		
DHDS-...-A [bar]	2	
DHDS-...-A-NC [bar]	4	
Max. operating pressure [bar]	8	
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)	
Ambient temperature ¹⁾ [°C]	+5 ... +60	
Corrosion resistance class CRC ²⁾	1	

- 1) Note operating range of proximity sensors
2) Corrosion resistance class 1 according to Festo standard 940 070
Components subject to low corrosion stress. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.


Weight [g]			
Size	16	32	50
DHDS-...-A	96	276	920
DHDS-...-A-NC	99	281	932

Three-point grippers DHDS

Technical data

Materials


Sectional view



Three-point gripper


1	Gripper jaw	High-alloy stainless steel
2	Cover cap	Polyamide
3	Reversing lever	Hardened sintered steel
4	Housing	Hard anodised wrought aluminium alloy
5	Piston	Polyacetal
-	Note on materials	Free of copper and PTFE
-		RoHS-compliant

Gripping force [N] at 6 bar



Size		16	32	50
Gripping force per gripper jaw				
DHDS-....A	Opening	40	135	280
	Closing	29	115	250
Total gripping force				
DHDS-....A	Opening	120	405	840
	Closing	87	345	750

Characteristic load values at the gripper jaws



The indicated permissible forces and torques apply to a single gripper jaw. They include the lever arm, additional applied loads due to the workpiece or external gripper fingers and acceleration forces occurring during movement.

The zero coordinate line (gripper finger point of rotation) must be taken into consideration for the calculation of torques.


Size	16	32	50
Max. permissible force F_z [N]	50	150	250
Max. permissible torque M_x [Nm]	2	9	24
Max. permissible torque M_y [Nm]	2	9	24
Max. permissible torque M_z [Nm]	2	9	24

Three-point grippers DHDS

Technical data

FESTO


Mass moment of inertia [kgcm²]



Mass moment of inertia of the three-point gripper in relation to the central axis, without external gripper fingers, without load.

Size	16	32	50
DHDS-...	0.14	0.79	6.10
DHDS-...-NC	0.14	0.82	6.18

Gripper jaw backlash





The plain-bearing guide used in the grippers means that there is backlash between the gripper jaws and the housing. The values entered in the table for the backlash were calculated in accordance with the traditional accumulative tolerance method.

Size	16	32	50
Max. gripper jaw backlash Sz [mm]	≤ 0.02		
Max. gripper jaw angular backlash ax, ay [°]	≤ 0.5	≤ 0.2	

Opening and closing times [ms] at 6 bar

Without external gripper fingers

With external gripper fingers



The indicated opening and closing times [ms] were measured at room temperature at an operating pressure of 6 bar with horizontally mounted grippers without additional gripper

fingers. The grippers must be throttled for greater applied loads. Opening and closing times must then be adjusted accordingly.


Size		16	32	50
Without external gripper fingers				
DHDS-...-A	Opening	26	44	62
	Closing	42	51	55
DHDS-...-A-NC	Opening	31	55	73
	Closing	34	47	50
With external gripper fingers per gripper finger (as a function of applied load)				
DHDS-...	1 N	100	–	–
	2 N	–	100	–
	3 N	–	200	100
	4 N	–	–	200
	5 N	–	–	300

Three-point grippers DHDS

Technical data

Gripping force F_H per gripper jaw as a function of operating pressure and lever arm x

The gripping forces as a function of operating pressure and lever arm can be determined from the following graphs.




— 2 bar
- - - 4 bar
- · - 6 bar
· · · 8 bar

Note


Gripper selection
sizing software
→ www.festo.com

External gripping (closing)


DHDS-16-A



DHDS-32-A



DHDS-50-A




Three-point grippers DHDS

Technical data

FESTO

Gripping force F_H per gripper jaw as a function of operating pressure and lever arm x

The gripping forces as a function of operating pressure and lever arm can be determined from the following graphs.




— 2 bar
 - - - 4 bar
 - · - 6 bar
 · · · 8 bar

Note


Gripper selection
 sizing software
 → www.festo.com

Internal gripping (opening)


DHDS-16-A



DHDS-32-A



DHDS-50-A





Three-point grippers DHDS

Technical data

Spring force F_F as a function of size and gripper jaw stroke l

Gripping force retention for DHDS-...-NC

The spring forces F_F as a function of gripper jaw stroke can be determined from the following graph.



Spring force F_F as a function of size, gripper jaw stroke l and lever arm x per gripper finger

The lever arm x must be taken into consideration when determining the actual spring force F_{Ftotal} . The formulae for calculating the spring force are provided in the table below.

Gripping force retention	Size	F_{Ftotal} per gripper finger
NC	16	$-0.1 \cdot x + 0.33 \cdot F_F$
	32	$-0.2 \cdot x + 0.33 \cdot F_F$
	50	$-0.3 \cdot x + 0.33 \cdot F_F$

Determination of the actual gripping forces F_{Gr} for DHDS-...-NC as a function of application per gripper finger

The three-point grippers with integrated spring type DHDS-...-NC (closing gripping force retention) can be used as:

- single-acting grippers

- grippers with supplementary gripping force and
- grippers with gripping force retention depending on requirements.

In order to calculate the available gripping forces F_{Gr} (per gripper finger), the gripping force (F_H) and spring force (F_{Ftotal}) must be combined accordingly.

Application forces per gripper finger

Single-acting	Supplementary gripping force	Gripping force retention
<ul style="list-style-type: none"> Gripping with spring force: $F_{Gr} = F_{Ftotal}$ Gripping with pressure force: $F_{Gr} = F_H - F_{Ftotal}$ 	<ul style="list-style-type: none"> Gripping with pressure and spring force: $F_{Gr} = F_H + F_{Ftotal}$ 	<ul style="list-style-type: none"> Gripping with spring force: $F_{Gr} = F_{Ftotal}$


Three-point grippers DHDS

Technical data

FESTO

Dimensions

Download CAD Data → www.festo.com/us/cad



Three-point grippers DHDS

Technical data

Size	B1	B2	B3	B4	B5	B6	B7	B8	B9
[mm]			±0.02	±0.5	±0.5	−0.02/−0.05	−0.02	−0.1	−0.1
16	13	19	11.5	20	17.5	7	6	9.96	5.75
32	13	36	19	28.5	24.6	8	10	–	–
50	25	54	30	43	37	12	14	–	–

Size	D1	D2	D3	D4	D5	D6	D7	D8	D9
[mm]	∅	∅ H8	∅ H8	∅ H8	∅ +0.05/+0.02		∅ h7	∅	
16	30	3	3.2	5	–	M3	5	3.2	M2.5
32	45	4	3.5	5	20	M3	5	3.2	–
50	70	5	6	7	30	M5	7	5.3	–

Size	EE	H1	H2	H3	H4	H5	H6	H7	H8 ¹⁾	H9
[mm]										
16	M3	60	47.9	32.6	4.5	24	21.5	3	6	12
32	M5	78	63.2	42.2	5.2	29	26	3.5	6.5	14.7
50	G ¹ / ₈	107.5	86.5	56	6.7	40	37	5	10	22

Size	H10	T1	T2	T3	T4	T5	T6	T7	T8	W1
[mm]		min.	min.	+1	−0.5	+0.1	±0.2		±1	
16	11	4.5	4.5	8	4	1.2	1	–	7	15°
32	10.5	6.5	6.5	10	4	1.1	0.5	8	–	30°
50	16	7	7	18	6	1.6	1	9	–	30°

1) Tolerance for centring hole ±0.02 mm
Tolerance for thread ±0.1 mm

Ordering data					
Size	Double-acting			Single-acting or with gripping force retention	
	without compression spring			Closing	
[mm]	Part No.	Type		Part No.	Type
16	1259491	DHDS-16-A		1259492	DHDS-16-A-NC
32	1259493	DHDS-32-A		1259494	DHDS-32-A-NC
50	1259495	DHDS-50-A		1259496	DHDS-50-A-NC

Three-point grippers DHDS

Accessories





FESTO

Adapter kit
HMSV, HAPG, HMVA, DHAA

Material:
Wrought aluminium alloy
Free of copper and PTFE
RoHS-compliant

Note

The kit includes the individual mounting interface as well as the necessary mounting material.

Permissible drive/gripper combinations with adapter kit				Download CAD Data → www.festo.com/us/cad		
Combination	Drive	Gripper	Adapter kit			
	Size	Size	CRC ¹⁾	Part No.	Type	
HMP/DHDS	HMP	DHDS	HMSV			
	Direct mounting					
	16, 20, 25	32	2	177765	HMSV-25	
	25, 32	50		177766	HMSV-26	
	Dovetail mounting					
	16, 20, 25	32	2	178212	HMSV-32	
	25, 32	50		178213	HMSV-33	
DGP ..., DGE-..., DGEA/DHDS	DG...	DHDS	HMVA, HAPG, HMSV			
	Direct mounting					
	18 ²⁾ , 25	16	2	196788	HMVA-DLA18/25	
				193921	HAPG-36-S3	
	40	16		196790	HMVA-DLA40	
			2	193921	HAPG-36-S3	
	Dovetail mounting					
	40	32		196790	HMVA-DLA40	
		2	178212	HMSV-32		
40	50		196790	HMVA-DLA40		
			178213	HMSV-33		
DRQD/DHDS	DRQD	DHDS	HAPG			
	8, 12	16	2	187569	HAPG-35	
	16	16		187567	HAPG-SD2-13	
	20	32		184481	HAPG-SD2-5	
	25	50		184484	HAPG-SD2-8	
	32	50		184487	HAPG-SD2-11	
	40, 50	50		526026	HAPG-SD2-20	
DRRD/DHDS	DRRD	DHDS	DHAA			
	16	16	2	2136626	DHAA-G-Q11-16-B4-16	
	16	32		2151381	DHAA-G-Q11-16-B4-32	
	20	32		2136339	DHAA-G-Q11-20-B4-32	
	25	32		1471583	DHAA-G-Q11-25-B4-32	
	25	50		1731165	DHAA-G-Q11-25-B4-50	
	32	50		1907040	DHAA-G-Q11-32-B4-50	
	35	50		2135899	DHAA-G-Q11-35-B4-50	

1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

2) Only for DGEA...

Three-point grippers DHDS






Accessories

Adapter kit
HMSV, HAPG, HMVA, DHAA

Material:
Wrought aluminium alloy
Free of copper and PTFE
RoHS-compliant

Note

The kit includes the individual mounting interface as well as the necessary mounting material.

Permissible drive/gripper combinations with adapter kit				Download CAD Data ➔ www.festo.com/us/cad	
Combination	Drive	Gripper	Adapter kit		
	Size	Size	CRC ¹⁾	Part No.	Type
HSP/DHDS	HSP	DHDS	HAPG		
	16	16	2	192705	HAPG-36-S1
				540882	HAPG-71-B
	25	16		192705	HAPG-36-S1
				540883	HAPG-72-B
HSW/DHDS	HSW	DHDS	HAPG		
	16	16	2	192705	HAPG-36-S1
				540882	HAPG-71-B
DSM/DHDS	DSM	DHDS	HAPG		
	8, 10	16	2	187569	HAPG-35
				163272	HAPG-23
	25	32			
EGSA/DHDS	EGSA	DHDS	HMSV		
	60	32	2	560019	HMSV-63
				177765	HMSV-25
ERMB/DHDS	ERMB	DHDS	HAPG		
	20	32	2	184481	HAPG-SD2-5
	25	50		184484	HAPG-SD2-8
	32	50		184487	HAPG-SD2-11

1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Three-point grippers DHDS

Accessories


FESTO

Adapter kit
HMSV, HAPG, HMVA, DHAA

Material:
Wrought aluminium alloy
Free of copper and PTFE
RoHS-compliant

Note


The kit includes the individual mounting interface as well as the necessary mounting material.

Permissible drive/gripper combinations with adapter kit				Download CAD Data ➔ www.festo.com/us/cad	
Combination	Drive	Gripper	Adapter kit		
	Size	Size	CRC ¹⁾	Part No.	Type
EHMB/DHDS	EHMB	DHDS	HAPG		
	20	50	2	184487	HAPG-SD2-11
	25, 32	50		526026	HAPG-SD2-20


- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Three-point grippers DHDS

Accessories



Ordering data						
	For size [mm]	Comment	Weight [g]	Part No.	Type	PU ¹⁾
Centring sleeve ZBH						
Technical data → Internet: zbh						
	16, 32	For centring the gripper fingers on the gripper jaws	1	189652	ZBH-5	10
	50		1	186717	ZBH-7	





1) Packaging unit

Ordering data				
Type	For size	Weight [g]	Part No.	Type
Position sensor SMH-S1			Technical data ➔ Internet: smh-s1	
	16	30	175713	SMH-S1-HGD16

Signal converter/evaluation unit for position sensor SMH-S1

Signal converter SVE4	Evaluation unit SMH-AE1
<ul style="list-style-type: none"> Converts analogue signals into switching points Switching function freely programmable with teach-in Threshold value, hysteresis or window comparator 	<ul style="list-style-type: none"> Converts analogue signals into switching points With 3 potentiometers for setting 3 switching points


Ordering data							
Type	For size	Input connection	Output connection	Switching output	Weight [g]	Part No.	Type
Signal converter SVE4						Technical data → Internet: sve4	
	16	Socket M8x1, 4-pin	Plug M8x1, 4-pin	2x PNP	19	544216	SVE4-HS-R-HM8-2P-M8
				2x NPN		544219	SVE4-HS-R-HM8-2N-M8
Evaluation unit SMH-AE1						Technical data → Internet: smh-ae	
	16	Socket M8x1, 4-pin	Plug M12x1, 5-pin	3x PNP	170	175708	SMH-AE1-PS3-M12
				3x NPN		175709	SMH-AE1-NS3-M12


Ordering data – Connecting cables				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
Connection between position sensor and signal converter/evaluation unit					
	Straight socket, M8x1, 4-pin	Straight plug, M8x1, 4-pin	2.5	554035	NEBU-M8G4-K-2.5-M8G4
Connection between evaluation unit and controller					
	Straight socket, M12x1, 5-pin	Cable, open end, 5-wire	2.5	541330	NEBU-M12G5-K-2.5-LE5
			5	541331	NEBU-M12G5-K-5-LE5
Connection between signal converter and controller					
	Straight socket, M8x1, 4-pin	Cable, open end, 4-wire	2.5	541342	NEBU-M8G4-K-2.5-LE4
			5	541343	NEBU-M8G4-K-5-LE4
	Angled socket, M8x1, 4-pin	Cable, open end, 4-wire	2.5	541344	NEBU-M8W4-K-2.5-LE4
			5	541345	NEBU-M8W4-K-5-LE4

Three-point grippers DHDS

Accessories

FESTO



Proximity sensor for size 32, 50						
Ordering data – Proximity sensors for T-slot, magneto-resistive					Technical data → Internet: smt	
	Type of mounting	Electrical connection, connection direction	Switching output	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot lengthwise	Cable, 3-wire, lateral	PNP	2.5	547859	SMT-8G-PS-24V-E-2,5Q-OE
		Plug M8x1, 3-pin, lateral		0.3	547860	SMT-8G-PS-24V-E-0,3Q-M8D

Proximity sensor for size 32, 50						
Ordering data – Position transmitters for T-slot					Technical data → Internet: smat	
	Type of mounting	Electrical connection, connection direction	Analogue output [V]	Cable length [m]	Part No.	Type
	Insertable in the slot from above	Plug M8x1, 3-pin, in-line	0 ... 10	0.3	553744	SMAT-8M-U-E-0,3-M8D

Note

Mode of operation:

The position transmitter continuously senses the position of the piston. It has an analogue output with an output signal in proportion to the piston position.

Ordering data – Connecting cables					Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type	
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541333	NEBU-M8G3-K-2.5-LE3	
			5	541334	NEBU-M8G3-K-5-LE3	
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541338	NEBU-M8W3-K-2.5-LE3	
			5	541341	NEBU-M8W3-K-5-LE3	

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com