


Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI



- 1 - Type to be discontinued
Available until 2012

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

FESTO

Key features



Innovative

- Multi-functional valve terminal in sturdy metal housing
- Electrical interlinking module for flexible expansion options

Standardised system of electrical connections:

- Multi-pin plug
- All common fieldbuses
- Integrated controllers for pre-processing

Suitable for electrical peripherals type 03 and CPX, i.e.:

- Diagnostics down to the individual valve
- Parameterisable error characteristics
- Separate load voltage supply for valves
- On-site diagnostics via LEDs or handheld terminal CPX (MMI)

Versatile

- Modular system offering a range of configuration options
 - Expandable up to 26 solenoid coils and 12 I/O modules
 - Conversions and extensions possible at a later date
 - Simple replacement of valves and valve functions
 - High pressure range -0.9 ... 10 bar
 - Wide range of valve functions
 - Multiple pressure zones
- Vertical stacking modules:
- Pressure regulator
 - Flow control plates

Reliable

Sturdiness:

- Metal valve housing
- Metal I/O module housing
- Electrical connection technology
- Fast troubleshooting thanks to LEDs on the valves and diagnostics via fieldbus
- Reliability of service through replaceable valves
- Manual override either non-detenting, detenting or covered
- Flexible labelling system thanks to inscription labels

In combination with CPX:

- Module and channel-specific diagnostics
- Comprehensive diagnostics on-site without PC, only with CPX-MMI

Easy to mount

- Ready-to-install and tested unit
- Sturdy mounting and version for harsh environments
- Lower selection, ordering, assembly and commissioning costs
- Wall mounting or H-rail mounting

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

Key features

Valve terminals type 03


Valve terminals are the most comprehensive system in intelligent pneumatics.

The multi-functional Festo valve terminals for MIDI/MAXI valves have a sturdy, modular design and they can be equipped with different valve sizes. A valve terminal can also have multiple pressure zones and vacuum operation as well as integrated pressure regulators and one-way flow control valves. The valve terminals are

therefore capable of providing versatile and flexible solutions to a wide variety of pneumatic control technology requirements, and the high-quality metal/plastic design and protection to IP65 mean that they can be effective even in the harshest operating environments.

A worldwide service and consultation network round off the performance spectrum.

Multi-pin plug variants




Valve terminals with multi-pin plug connections can be connected in the normal way to the I/O cards of all current control systems or industrial PCs. The central control system

requires a powerful PLC with a correspondingly high number of I/O cards and must also be connected to the fieldbus devices with more complex parallel wiring.

Festo offers several installation-saving multiple connection nodes and the appropriate multi-pin cables.

Connection types

Multi-pin plug




Round multi-pin plug connection, sturdy version for up to 24 solenoid coils.

Double multi-pin plug



Double round multi-pin plug connection for connecting up to 6 digital input modules for sensors.

Sub-D multi-pin plug connection



Sub-D multi-pin plug connection with protection to IP65, low-cost and flat, for up to 22 solenoid coils.

Control block with electrical I/O modules



Integrated controller and fieldbus interface, I/O modules as with fieldbus connection. Decentralised CP systems can also be connected.

Fieldbus node with electrical I/O modules



Communication and diagnostics with all common bus systems:

- Up to 12 sturdy type 03 I/O modules can be assembled
- Connection technology to IP65 with M12 or Sub-D plugs
- Digital I/O modules
- Analogue I/O modules
- Multi-functional I/O modules
- 2 A outputs for hydraulic valves

- 1 - Type to be discontinued
Available until 2012

FESTO

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

Key features

User documentation – GSD, EDS, etc.

Device description files and icons are used to explain the integration of the valve terminal type 03 in the configuration software of the various controller manufacturers.

These can be downloaded quickly and conveniently from the download area of the Festo website.

→ www.festo.com



Valve terminal configurator

Online via: → www.festo.com/us/engineering

The appropriate type 03 valve terminal can be chosen quickly and easily using the online catalogue. This includes an easy-to-use valve terminal configurator, which makes it much easier to order the right product.

The valve terminals are fully assembled according to your order specification and are individually tested. This reduces assembly and installation time to a minimum.

You order a valve terminal type 03 using the order code.

Ordering system for pneumatic components

→ Internet: type 03

Ordering system for electrical components

→ Internet: type 03, type 04

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

Peripherals overview

Electrical components



Flexible connection to the controller thanks to an extensive range of connection nodes:

- Multi-pin plug connection
- Fieldbus connection
- DeviceNet direct interface

Stand-alone solutions with integrated PLC (control block) from:

- Festo
- Allen Bradley

Electrical digital inputs/outputs:

- Max. 12 modules in combination with suitable nodes (see ordering data)
- Inputs for 24 V DC sensors, PNP or NPN outputs for small consuming devices 24 V DC
- High-current outputs up to 2 A PNP/NPN, for example for hydraulic valves, can be connected directly to the valve terminal

Proportional pneumatics:

- Analogue modules optimised for proportional valves, for example for Festo MPYE and MPPES for regulating the force of a cylinder
- To detect, control/regulate universal analogue variables (4 ... 20 mA or 0 ... 10 V) within the process – on-site to IP65

Optimising and expanding your application:

- Modules for installation-saving connection using sturdy Sub-D plugs to IP65
- Low-cost connections to input/output stations and operator units
- AS-interface master for connection to decentralised inputs/outputs covering an extensive range, for example in conveyor systems (type to be discontinued, do not use for new projects)
- Modules for connecting decentralised CPV and CPA valve terminals
- Extensions and supplements can be added at any time

Easy mounting:

- On H-rail
- On mounting surface
- With covers in welding environments

Simple servicing:

- LED display
- Manual override

Easy maintenance thanks to clip-on inscription fields.

Convenient diagnostics via fieldbus connection and integrated PLC:

- Status bits
- Diagnostic bits
- Integrated self-test

Detailed information on electrical peripherals:

→ Internet: type 03


- 1 - Type to be discontinued
Available until 2012

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

Peripherals overview

FESTO

Pneumatic components



Midi modules:

- Manifold block for two MIDI valves
- 500 l/min
- Up to cylinder diameter 63 mm

Maxi modules:

- Manifold block for two MAXI valves
- 1,250 l/min
- Up to cylinder diameter 80 mm

Valve actuation:

- All valves have an external pilot air supply and are therefore suitable for vacuum operation
- If the entire valve terminal is to be operated with a vacuum, the pilot air supply must be regulated and supplied externally
- If the pilot air supply is generated via one of the valve terminal's regulators, working pressure of > 4 bar must be applied to this compressed air supply
- All valves with non-detenting/detenting/blocked manual override (on request)

Additional modules:

- One-way flow control valves for setting the speed of travel separately with single and double-acting cylinders
- One-way flow control valves and pressure regulators can be fitted at working lines
- Intermediate pressure regulator plates for setting the contact pressure of a cylinder either at channel 1 or separately at channel 2 or 4

Flexible compressed air supply:

- Right-hand end plate with regulator for pilot air and flat plate silencer
- Additional compressed air supply with ducted exhaust air or integrated flat plate silencer
- Compressed air supply modules without regulator with externally regulated pilot air
- Multiple pressure zones, including vacuum, are possible for all valve sizes

Options:

- Vacant positions for subsequent extensions
- All connections also supplied with preassembled QS fittings (on request)
- All connections can also be supplied with an NPT thread

Service:


- Multiple valve sizes can be combined on a single terminal
- All valves can be replaced quickly and easily
- All valves are supplied with 1 or 2 LEDs
- All valves are ready for identification clips
- Flat design thanks to flat plate silencer
- Online valve terminal configurator available in the electronic catalogue or on the Internet

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

Peripherals overview

Multi-functional valve terminal

Components



- 1 Multi-pin node/fieldbus node/control block
- 2 Manifold block, size 4.0 (MIDI)
- 3 Adapter plate, size 4.0 to size 7.0, with regulator for auxiliary pilot air
- 4 Manifold block, size 7.0 (MAXI)
- 5 One-way flow control valve
- 6 Pressure regulator
- 7 Right-hand end plate
- 8 Additional compressed air supply with integrated silencer
- 9 Solenoid valve size 7.0 type MTH, JMTH
- 10 Port for ducted exhaust air
- 11 Solenoid valve size 4.0 type MT2H, JMT2H

Description

Valve terminals type 03 permit the combination of multiple valve sizes. This assures optimal adaptation to system requirements. The valves have a nominal size of 4.0 mm and 7.0 mm.

The transition from nominal size 4.0 mm (MIDI) to nominal size 7.0 mm

(MAXI) is made with an adapter plate. The adapter plate can only be used once in any given system. The MIDI valves must be mounted directly next to the nodes, followed by the MAXI valves.

Order:

- Nodes
- MIDI valves

- Adapter plate
- MAXI valves
- End plate

If no MIDI valves are used, the adapter plate must still be installed between the node and the first sub-base for MAXI valves.

Only valves with separate pilot air supply are used. Pilot pressure is supplied either via the adapter plate or the right-hand end plate. In either case, the maximum permissible pilot pressure is 5 bar. To limit the pilot pressure, special pressure regulators are provided on the adapter plate or the right-hand end plate.


Creating pressure zones

General information

A valve terminal can have multiple pressure zones and vacuum operation as well as integrated pressure regulators and one-way flow control valves.

For more than two pressure zones, multiple "compressed air supplies" or isolating discs can be combined. The isolating disc can only be inserted into a normal manifold block and not into the supply block.


MIDI



With MIDI valves, pressure zones for different pressures (including vacuum) are created via a "pressure zone supply" block.

The lower pressures should be supplied closest to the node.

MAXI



With MAXI valves, pressure zones are created by inserting an isolating disc. Air is then supplied via the adapter plate.

Additional power supply

Note

For valve terminals with more than ten valves and large-volume cylinders, at least one additional compressed air supply should be provided.


- 1 - Type to be discontinued
Available until 2012

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

Peripherals overview

FESTO

Vacuum operation



Note


If auxiliary pilot air is generated via one of the valve terminal's regulators, working pressure of > 4 bar must be applied to this compressed air supply.

If the entire valve terminal is to be operated with a vacuum, the pilot air supply must be regulated and supplied externally.

A filter must be installed upstream of valves operated in vacuum mode. This prevents any foreign matter in the intake air getting into the valve (e.g. when operating a suction cup).

Vertical stacking

General information



- 1 Solenoid valve
- 2 Pressure regulator
- 3 Manifold block
- 4 One-way flow control valve

Pressure regulator

A pressure regulator can be installed between the sub-base and the valve to influence the force of the actuated cylinder. There are three variants available:


- Regulation in port 1 (P)
- Regulation in port 2 (B)
- Regulation in port 4 (A)

One-way flow control valve

A block with one-way flow control valves can be mounted on the front of the sub-base to influence the speed of the controlled cylinder.


A block always contains 4 one-way flow control valves.

Pressure regulator at port 1 (P)




ILR-0,3-ZP-P-4,0
ILR-0,3-ZP-P-7,0

Pressure regulator at port 2 (B)




ILR-0,3-ZP-B-4,0
ILR-0,3-ZP-B-7,0

Pressure regulator at port 4 (A)



ILR-0,3-ZP-A-4,0
ILR-0,3-ZP-A-7,0

One-way flow control valve



IGR-0,3-AP-A/B-QS-6
IGR-0,3-AP-A/B-QS-8

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

Instructions for use

Equipment

Operate system equipment with unlubricated compressed air if possible. Festo valves and cylinders are designed so that, if used as designated, they will not require additional lubrication and will still achieve a long service life. The quality of compressed air downstream of the compressor must correspond to that of unlubricated compressed air. If possible, do not operate all of your system equipment with lubricated compressed air. The lubricators should, where possible, always be installed directly upstream of the actuator used.

Incorrect additional oil and too high an oil content in the compressed air reduce the service life of the valve terminal.

Use Festo special oil OFSW-32 or the alternatives listed in the Festo catalogue (as specified in DIN 51524 HLP32; basic oil viscosity 32 CST at 40 °C).

Bio-oils

When using bio-oils (oils which are based on synthetic or native ester, e.g. rapeseed oil methyl ester), the maximum residual oil content of 0.1 mg/m³ must not be exceeded (see ISO 8573-1 Class 2).

Mineral oils


When using mineral oils (e.g. HLP oils to DIN 51524, parts 1 to 3) or similar oils based on poly-alpha-olefins (PAO), the maximum residual oil content of 5 mg/m³ must not be exceeded (see ISO 8573-1 Class 4).

A higher residual oil content irrespective of the compressor oil cannot be permitted, as the basic lubricant would be flushed out over time.

Welding environment

Valve terminal type 03 has a high-quality metal/plastic design.


Suitable covers should be used to prevent the terminal being damaged as a result of welding spatter.


-  - Type to be discontinued
Available until 2012


Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

FESTO

Technical data – Valve terminal type 03 MIDI

-  - Flow rate up to
Type 03 MIDI:
300 ... 500 l/min
Type 03 MAXI:
1,250 l/min

-  - Valve width
Type 03 MIDI: 18 mm
Type 03 MAXI: 25 mm

-  - Voltage
24 V DC



| General technical data – Type 03 MIDI | | | | | | |
|---------------------------------------|---|------------------------|---|---|--|--|
| Valve function | 5/2-way valve | | | 5/3-way valve | | |
| | With pneumatic spring and pilot air supply | With mechanical spring | Double solenoid valve with pilot air supply | Mid-position closed with pilot air supply | Mid-position exhausted with pilot air supply | Mid-position pressurised with pilot air supply |
| Valve function order code | M, Y | L, Z | J | G | E | B |
| Design | Piston spool valve | | | | | |
| Width [mm] | 18 | | | | | |
| Nominal size [mm] | 4.0 | | | | | |
| Lubrication | Lubrication for life, silicon-free | | | | | |
| Type of mounting | On MIDI/MAXI valve terminal with 2 combi screws | | | | | |
| Mounting position | Any | | | | | |
| Manual override | Detenting | | | | | |
| Nominal flow rate [l/min] | 500 | 500 | 500 | 500 | 300 | 300 |

| Pressure ranges [bar] | | | | | | |
|--|--------------|------|---|---|---|---|
| Valve function order code | M, Y | L, Z | J | G | E | B |
| Operating pressure | -0.9 ... +10 | | | | | |
| Operating pressure for valve terminal with internal pilot air supply | 4 ... 8 | | | | | |
| Pilot pressure | 4 ... 6 | | | | | |

| Valve switching times [ms] | | | | | | | |
|----------------------------|------------|------|----|----|----|----|----|
| Valve function order code | M, Y | L, Z | J | G | E | B | |
| Switching times | On | 12 | 10 | - | 12 | 12 | 12 |
| | Off | 22 | 26 | - | 25 | 25 | 25 |
| | Changeover | - | - | 10 | - | - | - |
| Min. switching impulse | - | - | 7 | - | - | - | |

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

Technical data – Valve terminal type 03 MIDI

| Ambient conditions | |
|--|---|
| Operating medium | Filtered compressed air, lubricated or unlubricated → 9 |
| Grade of filtration [µm] | 40 |
| Storage temperature [°C] | -20 ... +40 |
| Ambient temperature [°C] | -5 ... +50 |
| Temperature of medium [°C] | -5 ... +50 |
| Corrosion resistance class CRC ¹⁾ | 2 |


- 1) CRC2: Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

| Electrical data | |
|--|--|
| Protection against electric shock (protection against direct and indirect contact to EN 60204-1/IEC 204) | By means of PELV power supply unit |
| Operating voltage [V DC] | 24 (+10/-15%) |
| Electrical power consumption per solenoid coil [W] | 1.5 |
| Protection class to EN 60529 | IP65 (for all types of signal transmission in assembled state) |
| Vibration resistance | To DIN/IEC 68/EN 60068, Parts 2-6 • With wall mounting: severity level 2 • With H-rail mounting: severity level 1 |
| Shock resistance | To DIN/IEC 68/EN 60068, Parts 2-27 • With wall mounting: severity level 2 • With H-rail mounting: severity level 1 |

- 1) The maximum signal line length is 10 m

| Materials | |
|-----------|--|
| Housing | Die-cast aluminium |
| Cap | Polyacetate, polyetheretherketone (PEEK), polyamide, steel |
| Seals | Nitrile rubber |

| Weight [g] | |
|-------------------------------|---------------|
| End plate without connections | 120 |
| Input modules | 360 |
| Multi-pin node | 580 |
| Blanking plate | 60 |
| Bus node | Approx. 1,000 |
| Output modules | 400 |
| Manifold block | 300 |
| Valve | 140 ... 160 |
| Pressure regulator | 100 |
| One-way flow control valve | 120 |

-  - Type to be discontinued
Available until 2012

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

FESTO

Technical data – Valve terminal type 03 MAXI

| General technical data – Type 03 MAXI | | | | | |
|---------------------------------------|---|---|---|--|--|
| Valve function | 5/2-way valve | | | 5/3-way valve | |
| | With pneumatic spring and pilot air supply | Double solenoid valve with pilot air supply | Mid-position closed with pilot air supply | Mid-position exhausted with pilot air supply | Mid-position pressurised with pilot air supply |
| Valve function order code | M, Y | J | G | E | B |
| Design | Piston spool valve | | | | |
| Width [mm] | 25 | | | | |
| Nominal size [mm] | 7 | | | | |
| Lubrication | Lubrication for life, silicon-free | | | | |
| Type of mounting | On MIDI/MAXI valve terminal with 2 combi screws | | | | |
| Mounting position | Any | | | | |
| Manual override | Detenting | | | | |
| Nominal flow rate [l/min] | 1,300 | | | | |

| Pressure ranges [bar] | | | | | |
|--|--------------|---|---|---|---|
| Valve function order code | M, Y | J | G | E | B |
| Operating pressure | -0.9 ... +10 | | | | |
| Operating pressure for valve terminal with internal pilot air supply | 4 ... 8 | | | | |
| Pilot pressure | 4 ... 6 | | | | |

| Valve switching times [ms] | | | | | | |
|----------------------------|------------|----|----|----|----|----|
| Valve function order code | M, Y | J | G | E | B | |
| Switching times | On | 25 | – | 25 | 25 | 25 |
| | Off | 30 | – | 55 | 55 | 55 |
| | Changeover | – | 18 | – | – | – |
| Min. switching impulse | 10 | 10 | 10 | 10 | 10 | |

| Ambient conditions | |
|--|---|
| Operating medium | Filtered compressed air, lubricated or unlubricated → 9 |
| Grade of filtration [µm] | 50 |
| Storage temperature [°C] | -20 ... +40 |
| Ambient temperature [°C] | -5 ... +50 |
| Temperature of medium [°C] | -5 ... +50 |
| Corrosion resistance class CRC ¹⁾ | 2 |

- 1) CRC2: Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

Technical data – Valve terminal type 03 MAXI

| Electrical data | |
|--|---|
| Protection against electric shock (protection against direct and indirect contact to EN 60204-1/IEC 204) | By means of PELV power supply unit |
| Operating voltage [V DC] | 24 (+10/-15%) |
| Electrical power consumption per solenoid coil [W] | 2.2 |
| Protection class to EN 60529 | IP65 (for all types of signal transmission in assembled state) |
| Vibration resistance | To DIN/IEC 68/EN 60068, Parts 2-6 <ul style="list-style-type: none"> • With wall mounting: severity level 2 • With H-rail mounting: severity level 1 |
| Shock resistance | To DIN/IEC 68/EN 60068, Parts 2-27 <ul style="list-style-type: none"> • With wall mounting: severity level 2 • With H-rail mounting: severity level 1 |





1) The maximum signal line length is 10 m

| Materials | |
|-----------|--|
| Housing | Die-cast aluminium |
| Cover | Polyacetate, polyetheretherketone (PEEK), polyamide, steel |
| Seals | Nitrile rubber |


| Weight [g] | |
|-------------------------------|---------------|
| End plate without connections | 435 |
| Input modules | 360 |
| Multi-pin node | 580 |
| Blanking plate | 63 |
| Bus node | Approx. 1,000 |
| Output modules | 400 |
| Manifold block | 552 |
| Valve | Approx. 313 |
| Pressure regulator | 188 |
| One-way flow control valve | 237 |

Connections

| Adapter plate | End plate | Pressure supply plate | Pressure zone supply module |
|---------------|-----------|-----------------------|-----------------------------|
|---------------|-----------|-----------------------|-----------------------------|





| Connection | 1 | 3/5 | 12/14 | 82/84 | Valves |
|------------|-----------------|-----------------|-----------------|-----------------|-----------------|
| MIDI | G $\frac{3}{8}$ | G $\frac{1}{2}$ | G $\frac{1}{8}$ | G $\frac{1}{8}$ | G $\frac{1}{8}$ |
| MAXI | G $\frac{1}{2}$ | G $\frac{1}{2}$ | G $\frac{1}{4}$ | G $\frac{1}{4}$ | G $\frac{1}{4}$ |

-  - Type to be discontinued
Available until 2012


Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

FESTO

Technical data – Valve terminal type 03, multi-pin plug

| Pin allocation – Multi-pin node with round plug MP1 | | | | | | | | |
|---|---|--------------------------|--------------------------|-----------------------------|---------|-------------------------|---------|--------------------------|
| View | Pin - plug | Wire - cable 14 wires | Wire - cable 26 wires | Solenoid coil ¹⁾ | | | | |
| | | | | Type PNP | | Type NPN | | |
| | | | | Coil | Voltage | Coil | Voltage | |
|  |  | 1 ... 12 | 1 ... 12 | 0 ... 11 | 24 V | 0 ... 11 | 0 V | |
| | | 13 ... 24 | – | 12 ... 23 | 24 V | 12 ... 23 | 0 V | |
| | | 25 ... 26 | 13 ... 14 | 25 ... 26 | – | 0 V (supply voltage) | – | 24 V (supply voltage) |

1) Counting mode for solenoid coils: starting from the multi-pin node from left to right and from top to bottom continuously.

| Pin allocation – Multi-pin node with round plug MP2 | | | | | | | |
|--|-------------------|--------------------------|-----------|---|----------|---|------|
| View | Pin - plug | Wire - cable 26 wires | Type PNP | | Type NPN | | |
| | | | Coil | Supply voltage | Coil | Supply voltage | |
|  | Plug on top | 1 ... 12 | 1 ... 24 | Solenoid coil ¹⁾ 0 ... 23 | – | Solenoid coil ¹⁾ 0 ... 23 | – |
| | | 25 ... 26 | 25 ... 26 | – | 0 V | – | 24 V |
| | Plug on underside | 1 ... 8 | 1 ... 8 | Input ²⁾ 0 ... 7 | – | Input ²⁾ 0 ... 7 | – |
| | | 9 | 9 | – | 0 V | – | 24 V |
| | | 10 | 10 | – | 24 V | – | 0 V |
| | | 25 ... 26 | 25 ... 26 | Input ²⁾ 8 ... 23 | – | Input ²⁾ 8 ... 23 | – |


1) Counting mode for solenoid coils: starting from the multi-pin node from left to right and from top to bottom continuously.


2) Counting mode for inputs: starting from the multi-pin node from left to right and from top to bottom continuously.

The 8-valve input module has two inputs on one terminal socket.

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

Technical data – Valve terminal type 03, multi-pin plug

| Pin allocation – Multi-pin node with Sub-D plug MP4 | | | | | |
|---|------------|-----------|--------------------|--------------------|--|
| View | Pin - plug | R/3 - pin | Signal | | |
| | | | Positive switching | Negative switching | |
|  | 1 | A1 | VSP0 | VSP0 | |
| | 2 | A2 | VSP1 | VSP1 | |
| | 3 | B1 | VSP2 | VSP2 | |
| | 4 | B2 | VSP3 | VSP3 | |
| | 5 | C1 | VSP4 | VSP4 | |
| | 6 | C2 | VSP5 | VSP5 | |
| | 7 | A3 | VSP6 | VSP6 | |
| | 8 | A4 | VSP7 | VSP7 | |
| | 9 | B3 | VSP8 | VSP8 | |
| | 10 | B4 | VSP9 | VSP9 | |
| | 11 | C3 | VSP10 | VSP10 | |
| | 12 | C4 | VSP11 | VSP11 | |
| | 13 | A5 | VSP12 | VSP12 | |
| | 14 | A6 | VSP13 | VSP13 | |
| | 15 | B5 | VSP14 | VSP14 | |
| | 16 | B6 | VSP15 | VSP15 | |
| | 17 | C5 | VSP16 | VSP16 | |
| | 18 | C6 | VSP17 | VSP17 | |
| | 19 | A7 | VSP18 | VSP18 | |
| | 20 | A8 | VSP19 | VSP19 | |
| | 21 | B7 | VSP20 | VSP20 | |
| | 22 | B8 | VSP21 | VSP21 | |
| | 23 | C7 | - | - | |
| | 24 | C10 | 0 V | 24 V | |
| | 25 | B10 | 0 V | 24 V | |
| Housing | A10 | - | Earthing | | |
| Housing | A9 | - | Earthing | | |

-  - Type to be discontinued
Available until 2012

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI


Technical data – Valve terminal type 03 MIDI/MAXI

FESTO

Dimensions

Download CAD Data → www.festo.com/us/cad

Valve terminal type 03 with multi-pin plug connection MP1



- | | | | |
|--|---|---|--|
| 1 Multi-pin node MP1 with round plug | 4 Pressure supply plate | 7 Pressure regulator | 10 Swivel bracket IBGH-03-7,0 (opened out) for connection to mounting rail |
| 2 Adapter plate MIDI + MAXI with pressure regulator for pilot pressure | 5 Mounting bracket (required every 200 mm with wall mounting) | 8 Left-hand end plate | |
| 3 Right-hand end plate | 6 One-way flow control valve | 9 Swivel bracket IBGH-03-4,0 (opened out) for connection to mounting rail | |



Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

Technical data – Valve terminal type 03 MIDI/MAXI


Dimensions

Download CAD Data → www.festo.com/us/cad

Valve terminal type 03 with multi-pin plug connection MP4



- | | | | |
|--|---|---|---|
| 1 Multi-pin node with Sub-D plug | 4 Compressed air supply plate | 7 Pressure regulator | 9 Swivel bracket IBGH-03-7,0 (opened out) for connection to mounting rail |
| 2 Adapter plate MIDI + MAXI with pressure regulator for pilot pressure | 5 Mounting bracket (required every 200 mm with wall mounting) | 8 Swivel bracket IBGH-03-4,0 (opened out) for connection to mounting rail | |
| 3 Right-hand end plate | 6 One-way flow control valve | | |

-  - Type to be discontinued
Available until 2012

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI



FESTO

Technical data – Valve terminal type 03 MIDI/MAXI

Dimensions

Download CAD Data → www.festo.com/us/cad

Valve terminal type 03 with multi-pin plug connection MP2



- | | | | |
|--|---|--|--|
| 1 8-valve input module | 5 Right-hand end plate | 9 Pressure regulator | 12 Swivel bracket IBGH-03-7,0 (opened out) for connection to mounting rail |
| 2 4-valve input module | 6 Compressed air supply plate | 10 End plate, left-hand | |
| 3 Multi-pin node MP2 with round plug | 7 Mounting bracket (required every 200 mm with wall mounting) | 11 Swivel bracket IBGH-03-4,0 (opened out) for connection to mounting rail | |
| 4 Adapter plate MIDI/MAXI with pressure regulator for pilot pressure | 8 One-way flow control valve | | |

- 2 - Type to be discontinued
Available until 2012

FESTO


Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

Technical data – Valve terminal type 03 MIDI/MAXI end plate


Dimensions

Download CAD Data → www.festo.com/us/cad

End plate, MIDI valves



End plate, MAXI valves




- 1 - Type to be discontinued
Available until 2012

FESTO

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

Technical data – Adjustable four-fold one-way flow control valve for MIDI/MAXI valves



- Compact valve manifold
- Direct attachment to the manifold block

These valves are used to regulate air flow, for example to control the piston speeds of single or double-acting cylinders. Non-return valves block air flow in one direction. Air is only able to flow via the cross section which is adjusted with the throttle screw. Air flows freely in the other direction through the open non-return valve.



| General technical data | | | |
|--|---------------------|---|----------------------------|
| Type | | IGR-03-A-P-A/B-QS-6 (MIDI) | IGR-03-A-P-A/B-QS-8 (MAXI) |
| Part No. | | 164947 | 164948 |
| Design | Flow control valve | Annular gap | |
| | Non-return function | Pressure relief gasket | |
| Width | [mm] | 36 | 50 |
| Nominal size | [mm] | 4.0 | 7.0 |
| Type of mounting | | On MIDI/MAXI valve terminal with 2 combi screws | |
| Mounting position | | Any | |
| Ambient temperature | [°C] | -10 ... +60 | |
| Temperature of medium | [°C] | -10 ... +60 | |
| Operating medium | | Filtered compressed air, lubricated or unlubricated → 9 | |
| Operating pressure | [bar] | 0.3 ... +10 | |
| Nominal flow rate in flow control direction, flow control valve open ¹⁾ | [l/min] | 270 | 570 |
| Nominal flow rate in return direction, flow control valve open ¹⁾ | [l/min] | 270 | 550 |
| Nominal flow rate in return direction, flow control valve closed | [l/min] | 200 | 350 |
| Weight | [g] | 120 | 237 |

1) 10 turns

| Materials | |
|-------------------|----------------|
| Housing | Aluminium |
| Regulating screws | Brass |
| Seals | Nitrile rubber |


Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

FESTO

Technical data – Adjustable four-fold one-way flow control valve for MIDI/MAXI valves

Control characteristic

Type IGR-03-...




- 1 - Type to be discontinued
Available until 2012

FESTO

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

Technical data – Pressure regulator for MIDI/MAXI valves



An adjustable pressure regulator can be installed between the sub-base and the valve in order to control the force of the actuated cylinder. This pressure regulator maintains an essentially constant output pressure (secondary side) independent of pressure fluctuations (primary side) and air consumption.



| General technical data (MIDI) | | | |
|-------------------------------|---|-----------------|-----------------|
| Type | ILR-03-ZP-P-4,0 | ILR-03-ZP-A-4,0 | ILR-03-ZP-B-4,0 |
| Part No. | 164941 | 164943 | 164945 |
| Design | Piston regulator | | |
| Width [mm] | 18 | | |
| Nominal size [mm] | 4.0 | | |
| Type of mounting | On MIDI/MAXI valve terminal with 2 combi screws | | |
| Mounting position | Any | | |
| Ambient temperature [°C] | -10 ... +60 | | |
| Temperature of medium [°C] | -10 ... +60 | | |
| Operating medium | Filtered compressed air, lubricated or unlubricated → 9 | | |
| Supply pressure [bar] | 0 ... +10 | | |
| Output pressure [bar] | 0 ... +8 | | |
| Weight [g] | 100 | | |


| General technical data (MAXI) | | | |
|-------------------------------|---|-----------------|-----------------|
| Type | ILR-03-ZP-P-7,0 | ILR-03-ZP-A-7,0 | ILR-03-ZP-B-7,0 |
| Part No. | 164942 | 164944 | 164946 |
| Design | Piston regulator | | |
| Width [mm] | 25 | | |
| Nominal size [mm] | 7.0 | | |
| Type of mounting | On MIDI/MAXI valve terminal with 2 combi screws | | |
| Mounting position | Any | | |
| Ambient temperature [°C] | -10 ... +60 | | |
| Temperature of medium [°C] | -10 ... +60 | | |
| Operating medium | Filtered compressed air, lubricated or unlubricated → 9 | | |
| Supply pressure [bar] | 0 ... +10 | | |
| Output pressure [bar] | 0 ... +8 | | |
| Weight [g] | 188 | | |

| Materials | |
|-----------|----------------|
| Housing | Aluminium |
| Seals | Nitrile rubber |

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

Technical data – Pressure regulator for MIDI/MAXI valves


Components




- 1 Pressure adjustment screw for 0 ... 8 bar range
- 2 Lock nut
- 3 Pressure indicator connection:
 - M3 (MIDI)
 - M5 (MAXI)


Flow rate characteristic

MIDI



MAXI



-  - Type to be discontinued
Available until 2012

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

FESTO

Technical data – Input module for multi-pin node

- Max. 24 inputs
- Input module for 24 V DC sensor signals
- M12 plug, single allocation connection technology with 4-valve modules, double allocation connection technology with 8-valve modules
- M12 plug, 4-pin
- The input statuses are indicated for each input signal on an assigned LED
- 24 V DC voltage supplied for all connected sensors
- Module width: 36 mm



Application

Application

Input modules enable the connection of cylinder sensors or other 24 V DC sensors (inductive, capacitive, etc.). Plugs with double allocation are separated using a DUO plug or DUO cable.

Overall power requirement

The overall power requirement for all connected sensors on a valve terminal must not exceed 2 A.

Sensor operation

If negative switching sensors are used, 24 V DC and 0 V DC must be swapped on the multi-pin node, i.e. 24 V DC must be applied to pin 3 on the sensor socket and 0 V DC must be applied to pin 1.

Pin allocations must therefore be checked before the sensors are connected. Positive switching sensors and negative switching sensors cannot be used together.

General technical data (MIDI)


| Type | VIGE-03-MP-4 | VIGE-03-MP-8 |
|-----------------------------------|--|-------------------------------|
| Part No. | 18 672 | 18 657 |
| No. of inputs | 4 | 8 |
| No. of occupied module positions | 1 | |
| Sensor connection type | 4 x M12, 4-pin socket with single allocation | Socket with double allocation |
| Max. power supply per channel [A] | 2 | |
| Max. sensor supply per module [A] | 2 | |
| Fuse protection for sensor supply | Central fuse 2 A, on system supply | |
| Sensor supply voltage [V DC] | 24 ± 10%, coming from multi-pin node | |
| Ambient temperature [°C] | -5 ... +50 | |
| Storage temperature [°C] | -20 ... +60 | |
| Material | Die-cast aluminium | |
| Protection class to EN 60 529 | IP65 | |
| Dimensions [mm] | 42 x 70 x 132 | |
| Weight [g] | 360 | |

Note

The input module for multi-pin node MP4/8 can only be used with the multi-pin variants of the valve terminal type 03. It cannot be used with type VIFB-03.

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

Technical data – Input module for multi-pin node








| Pin allocation – Inputs with multi-pin node | | | | | | | |
|---|---------------------------------|-----|------------|-----|------------|-----|---|
| View | Plug (from top to bottom) | Pin | MP4 | | MP8 | | |
| | | | Allocation | LED | Allocation | LED | |
|  | 1 | 1 | 24 V | 0 | 24 V | 0 | |
| | | 2 | Free | | lx +1 | | |
| | | 3 | 0 V | | 0 V | | 1 |
| | | 4 | lx | | lx | | |
| | 2 | 1 | 24 V | 1 | 24 V | 2 | |
| | | 2 | Free | | lx +1 | | |
| | | 3 | 0 V | | 0 V | | 3 |
| | | 4 | lx +1 | | lx +2 | | |
| | 3 | 1 | 24 V | 2 | 24 V | 4 | |
| | | 2 | Free | | lx +1 | | |
| | | 3 | 0 V | | 0 V | | 5 |
| | | 4 | lx +2 | | lx +4 | | |
| | 4 | 1 | 24 V | 3 | 24 V | 6 | |
| | | 2 | Free | | lx +1 | | |
| | | 3 | 0 V | | 0 V | | 7 |
| | | 4 | lx +3 | | lx +4 | | |

- 1 - Type to be discontinued
Available until 2012

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

FESTO

Ordering data – Accessories












| Ordering data | | | | |
|---|-----------------------------------|--|-----------------------|----------|
| | Code | Description | Type | Part No. |
| Solenoid valves MIDI | | | | |
|  | M/Y | 5/2-way valve, single solenoid, pneumatic spring return | MT2H-5/2-4,0-L-S-VI-B | 159 452 |
| | L/Z | 5/2-way valve, single solenoid, mechanical spring return | MT2H-5/2-4,0-S-VI-B | 159 454 |
| | J | 5/2-way valve, double solenoid | JMT2H-5/2-4,0-S-VI-B | 159 453 |
| | B | 5/3-way valve, mid-position pressurised | MT2H-5/3B-4,0-S-VI-B | 159 450 |
| | E | 5/3-way valve, mid-position exhausted | MT2H-5/3E-4,0-S-VI-B | 159 449 |
| | G | 5/3-way valve, mid-position closed | MT2H-5/3G-4,0-S-VI-B | 159 448 |
| Solenoid valves MAXI | | | | |
|  | M/Y | 5/2-way valve, single solenoid, pneumatic spring return | MTH-5/2-7,0-L-S-VI | 151 700 |
| | J | 5/2-way valve, double solenoid | JMTH-5/2-7,0-S-VI | 151 701 |
| | B | 5/3-way valve, mid-position pressurised | MTH-5/3B-7,0-S-VI | 151 704 |
| | E | 5/3-way valve, mid-position exhausted | MTH-5/3E-7,0-S-VI | 151 703 |
| | G | 5/3-way valve, mid-position closed | MTH-5/3G-7,0-S-VI | 151 702 |
| Right-hand end plate | | | | |
|  | R | With regulator MIDI | IEPR-03-4,0-LR | 18 781 |
| | H | Without regulator MIDI | IEPR-03-4,0-P | 18 645 |
|  | H | Without regulator MAXI | IEPR-03-7,0-P | 18 744 |
| | E | Without connections MIDI | IEPR-03-4,0 | 175 205 |
|  | E | Without connections MAXI | IEPR-03-7,0 | 18 749 |
| | One-way flow control valve | | | |
|  | Q | One-way flow control valve MIDI | IGR-03-AP-A/B-QS-6 | 164 947 |
| | Q | One-way flow control valve MAXI | IGR-03-AP-A/B-QS-8 | 164 948 |
| Pressure regulator | | | | |
|  | P | Port P MIDI | ILR-03-ZP-P-4,0 | 164 941 |
| | P | Port P MAXI | ILR-03-ZP-P-7,0 | 164 942 |
| | R | Port A MIDI | ILR-03-ZP-A-4,0 | 164 943 |
| | R | Port A MAXI | ILR-03-ZP-A-7,0 | 164 944 |
| | T | Port B MIDI | ILR-03-ZP-B-4,0 | 164 945 |
| | T | Port B MAXI | ILR-03-ZP-B-7,0 | 164 946 |

- 2 - Type to be discontinued
Available until 2012

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

FESTO

Ordering data – Accessories









| Ordering data | | | | |
|---|------|--|----------------------|----------|
| | Code | Description | Type | Part No. |
| Manifold block | | | | |
|  | | Single solenoid MIDI | VIGM-03-4,0 | 18 652 |
| | | Single solenoid MAXI | VIGM-03-7,0 | 18 742 |
| | | Double solenoid MIDI | VIGI-03-4,0 | 18 653 |
| | | Double solenoid MAXI | VIGI-03-7,0 | 18 743 |
| Adapter plate | | | | |
|  | XX | MIDI/MAXI | VIGP-03-7,0-4,0-LR | 18 748 |
| | WW | Without regulator | VIGP-03-7,0-4,0 | 18 740 |
|  | DD | Compressed air supply MIDI | VIGP-03-4,0 | 18 654 |
| | DD | Compressed air supply MAXI | VIGP-03-7,0 | 18 741 |
|  | HH | Compressed air supply with silencer MIDI | VIGP-03-4,0-U | 525 433 |
| | HH | Compressed air supply with silencer MAXI | VIGP-03-7,0-U | 525 435 |
| | NN | MIDI/MAXI with silencer | VIGP-03-7,0-4,0-U | 525 436 |
| | FF | MIDI/MAXI with regulator and silencer | VIGP-03-7,0-4,0-LR-U | 525 437 |
|  | UU | Additional pressure zone MIDI | VIGZ-03-4,0 | 18 638 |
| | VV | Additional pressure zone MIDI with silencer | VIGZ-03-4,0-U | 525 434 |
| Flat plate silencer | | | | |
|  | | Flat plate silencer MIDI | IU-03-4,0 | 165 635 |
| | | Flat plate silencer MAXI | IU-03-7,0 | 165 636 |
| Cover | | | | |
|  | C | Cover plate MIDI | IAP-03-4,0 | 18 648 |
| | A | Cover plate MAXI | IAP-03-7,0 | 18 745 |
| Mounting | | | | |
|  | B | For H-rail MIDI | IBGH-03-4,0 | 18 649 |
| | B | For H-rail MAXI | IBGH-03-7,0 | 18 747 |
|  | W | Mounting bracket | IBGW-03 | 18 678 |
| Small parts | | | | |
|  | S | Isolating disc MAXI | NSC-1/2-03-7,0 | 18 746 |
|  | | Inscription labels 9x20 in frames (20 pieces) | IBS-9x20 | 18 182 |
| | | Inscription labels 10x17 in frames (30 pieces) | IBS-10x17 | 160 238 |

- 1 - Type to be discontinued
Available until 2012

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

FESTO

Ordering data – Accessories


| Ordering data | | | | |
|---|------|--|------------------|----------|
| | Code | Description | Type | Part No. |
| Modules | | | | |
|  | F | Multi-pin input module, 4-valve | VIGE-03-MP-4 | 18 672 |
| | E | Multi-pin input module, 8-valve | VIGE-03-MP-8 | 18 657 |
| Plug | | | | |
|  | S | Plug, straight socket, M12, 4-pin, PG7 | SEA-GS-7 | 18 666 |
| | W | 4-pin, 2.5 mm ² O.D. | SEA-4GS-7-2,5 | 192 008 |
|  | X | Plug for 2 connecting cables, M12, PG11, 4-pin | SEA-GS-11-DUO | 18 779 |
| Cable | | | | |
|  | | DUO cable, 2x straight socket | KM12-DUO-M8-GDGD | 18 685 |
| | | DUO cable, straight/angled socket | KM12-DUO-M8-GDWD | 18 688 |
| | | DUO cable, 2x angled socket | KM12-DUO-M8-WDWD | 18 687 |
| Multi-pin plug connection | | | | |
|  | H | Connecting cable for multi-pin node MP4, with Sub-D connection, 5 m | KEA-1-25P-5 | 177 413 |
| | J | Connecting cable for multi-pin node MP4, with Sub-D connection, 10 m | KEA-1-25P-10 | 177 414 |
| | | Connecting cable for multi-pin node MP4, with Sub-D connection, x length | KEA-1-25P-X | 177 415 |
|  | | Connecting cable, 26-pin, for inputs, 10 m | KMP2-03-E-10-26 | 175 665 |
| | | Connecting cable, 26-pin, for valves, 10 m | KMP2-03-V-10-26 | 175 667 |
|  | E | Plug socket for multi-pin node MP2, 25-pin | SD-SUB-D-BU25 | 18 709 |
|  | Y | Multi-pin plug socket for multi-pin node MP2, for valves | IMP2-SD-26-V | 18 664 |
| | Q | Multi-pin plug socket for multi-pin node MP2, for inputs/outputs | IMP2-SD-26-EA | 18 665 |

- 1 - Type to be discontinued
Available until 2012

Valve terminals type 03 VIMP-/VIFB-03, multi-functional MIDI/MAXI

FESTO

Ordering data – Accessories

| Ordering data | | | | | |
|---|------------------------------------|------------------------------|----------|---------------------|----------|
| | Description | Allocation | Language | Type | Part No. |
| Manual | | | | | |
|  | Manual for valve terminals type 03 | Type 03 Pneumatics MIDI/MAXI | German | PBE-MIDI/MAXI-03-DE | 152 770 |
| | | | English | PBE-MIDI/MAXI-03-EN | 152 771 |
| | | | Spanish | PBE-MIDI/MAXI-03-ES | 163 917 |
| | | | French | PBE-MIDI/MAXI-03-FR | 163 937 |
| | | | Italian | PBE-MIDI/MAXI-03-IT | 165 441 |
| | | | Swedish | PBE-MIDI/MAXI-03-SV | 165 471 |

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com