

Parallel kinematic robots EXPT, tripod

FESTO



Parallel kinematic robots EXPT, tripod

Key features

FESTO

At a glance

The high-speed handling unit with robot functionality for free movement in three dimensions provides precision in movement and positioning as well as a high dynamic response of up to 150 picks/min.

The highly rigid mechanical design and low moving mass make the parallel kinematic robot with toothed belt axes in delta arrangement up to three times as fast as comparable Cartesian systems.

Three double rods keep the front unit horizontal at all times. The axes and servo motors do not move with the unit.

The parallel kinematic robots are suitable for handling loads of up to max. 5 kg.


Typical applications include:

- Picking & placing small parts
- Bonding
- Labelling
- Palletising
- Sorting
- Grouping
- Repositioning and separating

Comparison between parallel kinematic and Cartesian systems


Parallel kinematic robot

- Low moving mass – ideal for demanding requirements on dynamic response in three dimensions
- High path accuracy with a range of path profiles, even for highly dynamic operation
- Four sizes with a working space diameter of up to 1,200 mm



Cartesian system

- Axes build on one another; the first axis carries all the subsequent axes
- High moving mass, therefore much lower dynamic response
- Rectangular, scalable working space
- Based on standard components
- Flexible designs



Parallel kinematic robots EXPT, tripod

Key features

The technology in detail

Parallel kinematic robot

- 1 Mounting frame
- 2 Mounting bracket for toothed belt axis
- 3 Motor
- 4 Connection block
- 5 Rod pair
- 6 Interface housing
- 7 Angle kit → 37
- 8 Protective conduit → 37
- 9 Toothed belt axis
- 10 Tubing holder → 37
- 11 Front unit for attaching a gripper, etc. → 25



Front unit

→ 25

The front unit can optionally be ordered via the modular product system.

It includes a geared motor that enables rotary movement (fourth axis) and is available in two sizes.

The front unit can also be chosen with or without rotary through-feed, for vacuum or excess pressure.

A range of grippers can be attached to it → 38.




Installation type: Protected version (P8)


→ 32

A variant P8, where the axes are installed turned (slide on top), is available for the sizes 95 and 120. Abraded particles can form at the toothed belt; these particles therefore mostly collect in the axis and do not fall into the working space.

Standard



Protected version (P8)






Parallel kinematic robots EXPT, tripod

Key features

FESTO

Available working space

There are four sizes available with different working space diameters. In simplified terms, the possible working space can be described using the shape of a cylinder (→ drawing on the right). The more working space required, the smaller its diameter (→ graph below).



— EXPT-45
 - - - EXPT-70
 . . . EXPT-95
 - . - EXPT-120


Motor mounting variants

The attachment position of the motors can be individually configured via the modular product system (→ 32). The standard motor attachment position corresponds to code HHH (cf. illustration below). This means: A1/A2/A3 rear.


If a motor is to be attached on the front, a 'V' must be specified in the order code for the respective axis.

Code	Description
HHH	A1/A2/A3 rear
HHV	A3 front; A1/A2 rear
HVH	A2 front; A1/A3 rear
HVV	A2/A3 front; A1 rear
VHH	A1 front; A2/A3 rear
VHV	A1/A3 front; A2 rear
VVH	A1/A2 front; A3 rear
VVV	A1/A2/A3 front

The position of the interface housing depends on the position of the motor (V or H) on axis A1.



Coordinate system



Parallel kinematic robots EXPT, tripod

Key features

FESTO

Control system CMCA

The control system CMCA is suitable for the parallel kinematic robot EXPT. It is available in two variants:


- Mounting plate
- Mounting plate in the control cabinet housing

Can be ordered via the modular product system → 32 or separately
→ Internet: cmca


The control system includes the multi-axis controller CMXR and the motor controller CMMP required for activation. In addition, a safety circuit is also integrated, which together with the teach pendant CDSA represents the basic functionality.

The version with the control cabinet housing also features control elements and fans in the door. The control system CMCA is pre-programmed and already tested together with the relevant parallel kinematic robot.

Mounting plate



Mounting plate in the control cabinet housing



Relationship between the order code of the parallel kinematic robot EXPT and the control system CMCA

Depending on the configured parallel kinematic robot EXPT

- with or without front unit
- variant of the control system
- controller type

the order codes for the control system CMCA are as follows:

Allocation table	
Parallel kinematic robot EXPT	Control system CMCA
For mounting plate	
EXPT-...-T0-...-C-C1-...	CMCA-K1-C1-A4-C-S1
EXPT-...-T0-...-C-C2-...	CMCA-K1-C2-A4-C-S1
EXPT-...-T1 to T4-...-C-C1-...	CMCA-K1-C1-A5-C-S1
EXPT-...-T1 to T4-...-C-C2-...	CMCA-K1-C2-A5-C-S1
For mounting plate in the control cabinet housing	
EXPT-...-T0-...-CC-C1-...	CMCA-K1-C1-A4-CC-S1
EXPT-...-T0-...-CC-C2-...	CMCA-K1-C2-A4-CC-S1
EXPT-...-T1 to T4-...-CC-C1-...	CMCA-K1-C1-A5-CC-S1
EXPT-...-T1 to T4-...-CC-C2-...	CMCA-K1-C2-A5-CC-S1

Parallel kinematic robots EXPT, tripod

FESTO

Type codes

		EXPT	-	70	-	E1	-	T2	-	HHH	-	
Type												
EXPT	Parallel kinematic robot											
Working space [mm]												
45	Ø 450, H100											
70	Ø 700, H100											
95	Ø 950, H100											
120	Ø 1,200; H100											
Drive												
E1	DGE-25											
E4	EGC-80											
Attachment components												
T0	Without rotary drive											
T1	Rotary drive, size 8											
T2	Rotary drive, size 8 with pneumatic rotary through-feed											
T3	Rotary drive, size 11											
T4	Rotary drive, size 11 with pneumatic rotary through-feed											
Motor attachment position												
HHH	A1/A2/A3 rear											
HHV	A3 front; A1/A2 rear											
HVH	A2 front; A1/A3 rear											
HVV	A2/A3 front; A1 rear											
VHH	A1 front; A2/A3 rear											
VHV	A1/A3 front; A2 rear											
VVH	A1/A2 front; A3 rear											
VVV	A1/A2/A3 front											
Particle protection												
-	Standard											
P8	Protected version											

Parallel kinematic robots EXPT, tripod

Type codes

➔

CC	-	C1	-	B	-	15K	-	S	-	DE
----	---	----	---	---	---	-----	---	---	---	----

Control system	
-	None
C	Mounting plate
CC	Control cabinet

Multi-axis controller	
-	None
C1	With CMXR C1
C2	With CMXR C2, with integrated PLC

Operator terminal	
-	None
B	With teach pendant CDSA

Cable length	
-	None
5K	5 m
10K	10 m
15K	15 m


Presetting	
-	Standard
S	With calibration

Documentation in the languages	
DE	German
EN	English
ES	Spanish
FR	French
IT	Italian
RU	Russian
SV	Swedish
ZH	Chinese

Parallel kinematic robots EXPT, tripod

Peripherals overview

FESTO



Parallel kinematic robots EXPT, tripod

Peripherals overview

FESTO

Attachments and accessories		
Type	Description	→ Page/Internet
1 Connecting cable 5K, 10K, 15K	All required connecting cables/tubing are included in the delivery as loose parts. The required cable length can be selected in the modular product system (none, 5 m, 10 m or 15 m)	36
2 Servo motor HHH, HHV, ...	The attachment position of the motors can be defined via the modular product system (HHH ... VVV). No homing required thanks to a multi-turn rotary encoder	–
3 Front unit T0, T1, T2, ...	Choose from: <ul style="list-style-type: none"> • Front unit without rotary drive (T0) • Front unit with rotary drive (T1 to T4) 	–
4 Interface housing	Serves as the interface between the parallel kinematic robot and the control cabinet, to supply the front unit	–
5 Protective conduit MKG	Is pre-assembled for all variants (T0 to T4), on axis A1	37
6 Angle kit EAHM-E10	Is pre-assembled for all variants (T0 to T4), on axis A1. If required, further angle kits can be ordered as accessories	37
7 Tubing holder EAHM-E10-TH	Is pre-assembled for all variants (T0 to T4), on axis A1. If required, further tubing holders can be ordered as accessories	37
8 Front unit installation	The lines to supply the front unit are already installed between the front unit and the interface housing	–

Parallel kinematic robots EXPT, tripod

Technical data

FESTO

-N- Size 45, 70, 95, 120 www.festo.com/en/Spare_parts_service



General technical data					
Size		45	70	95	120
Design		Parallel kinematic robot			
Motor type		Servo motor			
Mounting position		Horizontal			
Working space					
Nominal diameter	[mm]	450	700	950	1,200
Nominal height	[mm]	100	100	100	100
Max. acceleration ¹⁾	[m/s²]	110			
Max. speed ¹⁾	[m/s]	7			
Max. pick rate ¹⁾²⁾	[picks/min]	150			
Repetition accuracy	[mm]	±0.1			
Positioning accuracy ³⁾	[mm]	±0.5			
Track precision ³⁾⁴⁾	[mm]	±0.5			
Effective load ⁵⁾					
With min. dynamic response	[kg]	5			
With max. dynamic response	[kg]	1			
Base weight	[kg]	45	47.5	61.5	66

1) When used in combination with motor controller CMMP-AS-C5-3A and multi-axis controller CMXR.

2) In the 12° cycle.

3) Only with calibrated system (order code S).

4) At a speed of ≤0.3 m/s.

5) Total of the load mass and the accessories mounted on the front unit.

Max. process force in Z direction					
Size		45	70	95	120
With working space diameter	[mm]	0	0	0	0
Process force	[N]	1,300	1,000	1,000	850
With working space diameter ⁶⁾	[mm]	112.5	175	237.5	300
Process force	[N]	1,000	750	750	750

6) The specified values correspond to 25% of the nominal diameter.

Operating and environmental conditions		
Ambient temperature	[°C]	0 ... +40
Storage temperature	[°C]	-10 ... +60
Operating pressure for rod loss detection	[bar]	2 ... 8
Duty cycle ⁷⁾	[%]	100
Corrosion resistance class CRC ⁸⁾		2

7) When used in combination with motor controller CMMP-AS-C5-3A and multi-axis controller CMXR.

8) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.


Parallel kinematic robots EXPT, tripod

Technical data

FESTO

Materials


Sectional view



Parallel kinematic robot

1	Mounting frame	Wrought aluminium alloy
2	Toothed belt axis DGE/EGC	→ Internet: dge, egc
3	Ball stud	Wrought aluminium alloy
4	Tension spring	High-alloy stainless steel
5	Rod pair	Plastic, carbon-fibre reinforced
6	Ball cup	Polyamide
	Ball	Ceramic
7	Front unit	Wrought aluminium alloy
-	Note on materials	Contains PWIS (paint-wetting impairment substances)
		Free of copper and PTFE

Rod loss detection




The rod loss detection feature detects detached rods and initiates an emergency stop.

It is realised via permanent compressed air monitoring (pressure switch integrated in the frame of the interface housing)

This is done by pressurising the ball cup connections of the front unit with compressed air at 2 bar (rel.).

Connections on the interface housing:



1 Compressed air supply for rod loss detection.
The compressed air is adjusted to 2 bar in the interface housing.



2 Pressure sensor for monitoring rod loss detection.
Connecting cable → 32

Pick rate as a function of effective load

The characteristic values for dynamic response are determined in so-called 12" cycles. The graph below shows the maximum number of possible cycles as a function of effective load. It is based on an accuracy of ± 0.5 mm.

One 12" cycle means:

1. To the gripping position
2. To the start position
3. To the transfer position
4. To the set down position
5. To the transfer position
6. To the start position




n= Cycles per minute
m= Effective load

Parallel kinematic robots EXPT, tripod

Technical data

FESTO


Max. acceleration a as a function of position in the working space R and distance l from the centre of gravity of the effective load m to the front unit



1 Centre of gravity


EXPT-45

Effective load of 0.1 kg




— $a = 0 \dots 100 \text{ m/s}^2$

Effective load of 0.5 kg



— $a = 0 \dots 100 \text{ m/s}^2$

Effective load of 1 kg




— $a = 0 \dots 70 \text{ m/s}^2$

--- $a = 100 \text{ m/s}^2$

— $a = 90 \text{ m/s}^2$

--- $a = 80 \text{ m/s}^2$

Effective load of 1.5 kg



— $a = 0 \dots 50 \text{ m/s}^2$

--- $a = 80 \text{ m/s}^2$


— $a = 70 \text{ m/s}^2$

--- $a = 60 \text{ m/s}^2$

Parallel kinematic robots EXPT, tripod


Technical data

Max. acceleration a as a function of position in the working space R and distance l from the centre of gravity of the effective load m to the front unit




EXPT-45

Effective load of 2 kg




— $a = 0 \dots 40 \text{ m/s}^2$
- - - $a = 60 \text{ m/s}^2$
- · - $a = 50 \text{ m/s}^2$

Effective load of 3 kg




— $a = 0 \dots 30 \text{ m/s}^2$
- - - $a = 40 \text{ m/s}^2$

Effective load of 4 kg



— $a = 0 \dots 20 \text{ m/s}^2$
- - - $a = 30 \text{ m/s}^2$

Effective load of 5 kg




— $a = 0 \dots 10 \text{ m/s}^2$
- - - $a = 30 \text{ m/s}^2$
- · - $a = 20 \text{ m/s}^2$

Parallel kinematic robots EXPT, tripod

Technical data

FESTO


Max. acceleration a as a function of position in the working space R and distance l from the centre of gravity of the effective load m to the front unit



1 Centre of gravity


EXPT-70

Effective load of 0.1 kg




$a = 0 \dots 100 \text{ m/s}^2$

Effective load of 0.5 kg



$a = 0 \dots 100 \text{ m/s}^2$

Effective load of 1 kg




$a = 0 \dots 70 \text{ m/s}^2$

$a = 100 \text{ m/s}^2$

$a = 90 \text{ m/s}^2$

$a = 80 \text{ m/s}^2$

Effective load of 1.5 kg



$a = 0 \dots 50 \text{ m/s}^2$

$a = 80 \text{ m/s}^2$


$a = 70 \text{ m/s}^2$

$a = 60 \text{ m/s}^2$

Parallel kinematic robots EXPT, tripod

Technical data


Max. acceleration a as a function of position in the working space R and distance l from the centre of gravity of the effective load m to the front unit



1 Centre of gravity


EXPT-70

Effective load of 2 kg




— $a = 0 \dots 40 \text{ m/s}^2$
 - - - $a = 60 \text{ m/s}^2$
 - · - $a = 50 \text{ m/s}^2$

Effective load of 3 kg




— $a = 0 \dots 30 \text{ m/s}^2$
 - - - $a = 40 \text{ m/s}^2$

Effective load of 4 kg



— $a = 0 \dots 20 \text{ m/s}^2$
 - - - $a = 30 \text{ m/s}^2$

Effective load of 5 kg




— $a = 0 \dots 10 \text{ m/s}^2$
 - - - $a = 30 \text{ m/s}^2$
 - · - $a = 20 \text{ m/s}^2$

Parallel kinematic robots EXPT, tripod

Technical data

FESTO


Max. acceleration a as a function of position in the working space R and distance l from the centre of gravity of the effective load m to the front unit



1 Centre of gravity


EXPT-95

Effective load of 0.1 kg




— $a = 0 \dots 100 \text{ m/s}^2$

Effective load of 0.5 kg



— $a = 0 \dots 100 \text{ m/s}^2$

Effective load of 1 kg



— $a = 0 \dots 60 \text{ m/s}^2$


--- $a = 100 \text{ m/s}^2$

— $a = 90 \text{ m/s}^2$

--- $a = 80 \text{ m/s}^2$

--- $a = 70 \text{ m/s}^2$

Effective load of 1.5 kg



— $a = 0 \dots 50 \text{ m/s}^2$

--- $a = 80 \text{ m/s}^2$


— $a = 70 \text{ m/s}^2$

--- $a = 60 \text{ m/s}^2$

Parallel kinematic robots EXPT, tripod


Technical data

Max. acceleration a as a function of position in the working space R and distance l from the centre of gravity of the effective load m to the front unit




EXPT-95


Effective load of 2 kg




Effective load of 3 kg



Effective load of 4 kg



Effective load of 5 kg




Parallel kinematic robots EXPT, tripod

Technical data

FESTO


Max. acceleration a as a function of position in the working space R and distance l from the centre of gravity of the effective load m to the front unit



1 Centre of gravity


EXPT-120

Effective load of 0.1 kg




— $a = 0 \dots 100 \text{ m/s}^2$

Effective load of 0.5 kg




— $a = 0 \dots 100 \text{ m/s}^2$

Effective load of 1 kg



— $a = 0 \dots 60 \text{ m/s}^2$
 - - - $a = 100 \text{ m/s}^2$
 - - - $a = 90 \text{ m/s}^2$
 - - - $a = 80 \text{ m/s}^2$
 - - - $a = 70 \text{ m/s}^2$

Effective load of 1.5 kg




— $a = 0 \dots 50 \text{ m/s}^2$
 - - - $a = 80 \text{ m/s}^2$
 - - - $a = 70 \text{ m/s}^2$
 - - - $a = 60 \text{ m/s}^2$

Parallel kinematic robots EXPT, tripod

Technical data


FESTO

Max. acceleration a as a function of position in the working space R and distance l from the centre of gravity of the effective load m to the front unit




EXPT-120

Effective load of 2 kg




— $a = 0 \dots 40 \text{ m/s}^2$
 - - - $a = 60 \text{ m/s}^2$
 - · - $a = 50 \text{ m/s}^2$

Effective load of 3 kg




— $a = 0 \dots 20 \text{ m/s}^2$
 - - - $a = 40 \text{ m/s}^2$
 - · - $a = 30 \text{ m/s}^2$

Effective load of 4 kg



— $a = 0 \dots 20 \text{ m/s}^2$
 - - - $a = 30 \text{ m/s}^2$

Effective load of 5 kg



— $a = 0 \dots 10 \text{ m/s}^2$
 - - - $a = 30 \text{ m/s}^2$
 - · - $a = 20 \text{ m/s}^2$

Parallel kinematic robots EXPT, tripod

Technical data

FESTO

Requirements for the frame

The positioning and path accuracy depends to a large extent on the frame design.

The following influences must therefore be taken into consideration:

- Frame rigidity
- Frame mass
- Parallel kinematic robot mass

- Start-up frequency caused by dynamic operation of the parallel kinematic robot
 - Cycles per minute
 - Dynamic settings for acceleration and jerk

Maximum forces occur if two axes accelerate in the opposite direction to the third and result in horizontal movement of the effective load.

The frame must be designed so that the maximum forces that can occur as a result of the parallel kinematics can be absorbed with the necessary degree of certainty.

The guide value for the first natural frequency is specified for the complete system of at least 16 Hz.

At maximum dynamic response for the axes, the following forces act on the corner bracket and therefore on the mounting in the frame.

Size		45	70	95	120
Vertical force	[N]	±250	±290	±325	±475
Horizontal force	[N]	±145	±150	±200	±215

Mounting options on the frame


The kinematic structure must always be mounted in the area of the corner bracket of the mounting frame. Ensure that the corner bracket area has a torsionally rigid, flat bearing surface.

The bearing surface must meet the following minimum requirements in order to achieve the positioning accuracy:

- Flatness = 0.05 mm
- Parallelism = 0.5 mm

Since the distance between slots is 40 mm in the 80x80 profile, the holes in the corner brackets are positioned so that the profile can be mounted in various positions.

Since axis homing settings are lost when the motor is dismounted, it is recommended to use mounting holes that do not require the motor to be removed.


The holes  are not accessible, depending on the attachment position of the motor.

Direct mounting via screws

Screws M8x...


Via at least 4 screws (M8) per corner bracket directly on the frame. These 4 screws should be placed as far apart

as possible to ensure a torsionally rigid connection.



Screws M20x...

Via 1 screw (M20) per corner bracket directly on the frame. There is a central hole for this purpose on every corner.



Parallel kinematic robots EXPT, tripod


Technical data

Mounting options on the frame


Mounting via slot nuts – parallel to the mounting frame

- | | |
|--|---------------------------------|
| 1 Profile
(e.g. HMBS-80/80) | 3 Screws
(e.g. M8x35) |
| 2 Slot nut
(e.g. NST-HMV-8-2-M8) | |

Example 1



Example 2




Mounting via slot nuts – at right angles to the mounting frame

- | | |
|--|---------------------------------|
| 1 Profile
(e.g. HMBS-80/80) | 3 Screws
(e.g. M8x35) |
| 2 Slot nut
(e.g. NST-HMV-8-2-M8) | 4 Bracket |


The additional angle brackets in the following examples are required in order to increase the torsional rigidity and the bearing surface.

Example 1

Profile mounting




Angle bracket mounting




Example 2

Profile mounting



Angle bracket mounting



Parallel kinematic robots EXPT, tripod

Technical data

FESTO

Technical data – Front unit

EXPT-...-T...



Mechanical data				
Type	EXPT-...-			
	T1	T2	T3	T4
Design	Electromechanical rotary module			
	–	With rotary through-feed	–	With rotary through-feed
Motor type	Servo motor			
Size	8	8	11	11
Rotation angle	Infinite			
Pneumatic connection	–	G $\frac{1}{8}$	–	G $\frac{1}{8}$
Nominal size [mm]	–	4	–	4
Standard nominal flow rate [l/min]	–	350	–	350
Gear ratio	30:1			
Repetition accuracy [°]	±0.01			
Max. output speed [rpm]	200			
Nominal torque [Nm]	0.75	0.75	1.8	1.8
Peak torque [Nm]	1.8	1.8	4.5	4.5
Max. axial force [N]	200	200	300	300
Max. pull-out torque, static [Nm]	15	15	40	40
Perm. mass moment of inertia of load [kgm ²]	0.0026	0.0026	0.006	0.006
Mounting position	Any			
Load mass for EXPT [g]	640	690	850	900

Electrical data				
Type	EXPT-...-			
	T1	T2	T3	T4
Nominal voltage [V AC]	230			
Nominal current [A]	0.31	0.31	0.74	0.74
Peak current [A]	0.61	0.61	1.5	1.5
Rated output [W]	9.2	9.2	22.1	22.1
Duty cycle [%]	100			
Measuring system ¹⁾	Encoder			

1) Homing required

Operating and environmental conditions				
Type	EXPT-...-			
	T1	T2	T3	T4
Operating pressure [bar]	–	–0.9 ... +10	–	–0.9 ... +10
Ambient temperature [°C]	0 ... 40			
Protection	IP40			
Note on materials	RoHS-compliant			
Corrosion resistance class CRC ¹⁾	2			


1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Parallel kinematic robots EXPT, tripod

Technical data

Connections on the interface housing





Connection for:

- 1 Encoder cable → 32
- 2 Sensor for rotary motion → 32
- 3 Supply port for pneumatic rotary through-feed
- 4 Motor cable → 32

Dimensions

Download CAD Data → www.festo.com/us/cad

Front unit



- 1 Supply port outlet
- 2 Supply port rotary through-feed
- 3 Connection for motor cable
- 4 Connection for encoder cable

Type	B1	B2	B3	D1 Ø H7	D2	D3 Ø	D4 Ø	H1	H2 +1	L1	L2	T1	T2
EXPT-...	141	122	88	7	M4	48	25	27	6	162	86	1.6	10

Parallel kinematic robots EXPT, tripod


Technical data

FESTO

Dimensions

Download CAD Data → www.festo.com/us/cad

Parallel kinematic robot



Type	B1	B2	B3	B4	H1	H2	H3	L1	L2
EXPT-45	947	617	530	549	659	493	166	1,088	652
EXPT-70	1,077	703	622	590	727	561	166	1,238	727
EXPT-95	1,213	794	705	626	827	636	191	1,394	803
EXPT-120	1,355	888	800	672	944	710	234	1,558	885

Parallel kinematic robots EXPT, tripod


Technical data

FESTO

Dimensions

Download CAD Data → www.festo.com/us/cad

Mounting holes on the mounting frame



Type	B1	B2	B3	B4	B5	B6	B7
EXPT-45	330.8	107.2	93.5	87.2	51	12.3	11
EXPT-70	374.1	107.2	93.5	87.2	51	12.3	11
EXPT-95	419.3	107.2	93.5	87.2	51	12.3	11
EXPT-120	466.6	107.2	93.5	87.2	51	12.3	11

Type	L1	L2	L3	L4	L5	L6	L7
EXPT-45	1,017	923	775.4	675.4	822	794	694.6
EXPT-70	1,167.1	1,073.1	925.5	825.5	972.1	914	844.7
EXPT-95	1,323.7	1,229.7	1,082.1	982.1	1,128.7	1,070.6	1,001.3
EXPT-120	1,487.5	1,393.5	1,245.9	1,145.9	1,292.5	1,234.4	1,165.1

Parallel kinematic robots EXPT, tripod


Technical data

FESTO

Dimensions

Download CAD Data → www.festo.com/us/cad

Interference contour within the operating area



- 1 Interference contour
- D3 Diameter of interference contour
- D4 Diameter of nominal operating area
- H7 Height of nominal operating area
- H9 Distance from bottom edge of gripper plate to base of nominal operating area

Note

The distance specification for the working space refers to the bottom edge of the gripper plate. With the variants T1 to T4, the working space is extended downwards by the dimension H8. The same applies to attached gripper systems, where the reference point is always shifted by the height of the gripper system. Additional dimensions for laying the motor cables and tubing are not taken into account in the interference contour.

Type	D1 ±5	D2 ±5	D3 ±5	D4	H1	H4	H5
EXPT-45	950	860	620	450	659	500	117
EXPT-70	1,120	1,035	870	700	727	614	117
EXPT-95	1,400	1,260	1,120	950	827	760	141
EXPT-120	1,590	1,440	1,370	1,200	944	907	141

Type	H6	H7	H8			H9
			EXPT-...-T0	EXPT-...-T1/T2	EXPT-...-T3/T4	
EXPT-45	180	100	0	27	28.5	234
EXPT-70	180	100	0	27	28.5	286
EXPT-95	170	100	0	27	28.5	357
EXPT-120	170	100	0	27	28.5	397


Parallel kinematic robots EXPT, tripod

Technical data


Pin allocations

Axis motor

Motor



Encoder




Pin	Function
1	Phase U
PE	PE (protective earth)
3	Phase W
4	Phase V
A	Temperature sensor M_T+
B	Temperature sensor M_T-
C	Holding brake BR+
D	Holding brake BR-


Pin	Function
1	-SENS
2	+SENS
3	DATA
4	DATA/
5	0 V
6	CLOCK/
7	CLOCK
8	UP

Front unit motor

Motor



Encoder



Pin	Function
1	U
2	V
3	W
4	PE

Pin	Function
1	A
2	A\
3	B
4	B\
5	Z
6	Z\
7	U
8	V
9	W
10	GND
11	5 V
12	Shield

Parallel kinematic robots EXPT, tripod

Ordering data – Modular products

FESTO

Ordering table							
Size	45	70	95	120	Condition s	Code	Enter code
[M]	Module No.	569797	569798	569799	569800		
	Product type	EXPT series T					EXPT
	Working space	[mm] 450	–			-45	
		[mm] –	700	–		-70	
		[mm] –	950		–	-95	
		[mm] –			1,200	-120	
	Drive	DGE-25		–		-E1	
		–		EGC-80		-E4	
	Attachment components	Without rotary drive				-T0	
		Rotary drive, size 8				-T1	
		Rotary drive, size 8 with pneum. air through-feed				-T2	
		Rotary drive, size 11				-T3	
		Rotary drive, size 11 with pneum. air through-feed				-T4	
	Motor attachment position	A1/A2/A3 rear				-HHH	
		A3 front, A1/A2 rear				-HHV	
		A2 front, A1/A3 rear				-HVH	
		A2/A3 front, A1 rear				-HVV	
		A1 front, A2/A3 rear				-VHH	
		A1/A3 front, A2 rear				-VHV	
		A1/A2 front, A3 rear				-VVH	
		A1/A2/A3 front				-VVV	
[O]	Particle protection	Standard					
		–		Protected version		-P8	

Transfer order code

	EXPT	–		–		–		–	
--	------	---	--	---	--	---	--	---	--

Parallel kinematic robots EXPT, tripod

Ordering data – Modular products

FESTO

Ordering table							
Size	45	70	95	120	Conditions	Code	Enter code
[O] Control system	None						
	Mounting plate					-C	
	Control cabinet					-CC	
	None						
	With CMXR-C1					-C1	
	With CMXR-C2, with integrated PLC					-C2	
	None						
	With teach pendant CDSA					-B	
	None						
	5 m					-5K	
Cable length	10 m					-10K	
	15 m					-15K	
Presetting	Standard						
	With calibration					-S	
[M] Documentation in the languages	German					DE	
	English					EN	
	Spanish					ES	
	French					FR	
	Italian					IT	
	Russian					RU	
	Swedish					SV	
	Chinese					ZH	

Note

To order a parallel kinematic robot, please get in touch with your local Festo contact person.

The parallel kinematic robots may only be commissioned by a specially trained technician (robotics specialist).

The following knowledge is required:

- Specialist knowledge of robotics and CoDeSys
- Knowledge of handling motor controllers CMMP and multi-axis controllers CMXR
- Knowledge of handling parallel kinematic systems






Transfer order code

- - - - - -

Parallel kinematic robots EXPT, tripod

Accessories




FESTO

Ordering data			
	Cable length [m]	Part No.	Type
Connection from axis motor to motor controller in the control cabinet			
	Motor cable NEBM		
	5	550310	NEBM-M23G6-E-5-N-LE7
	10	550311	NEBM-M23G6-E-10-N-LE7
	15	550312	NEBM-M23G6-E-15-N-LE7
	X length ¹⁾	550313	NEBM-M23G6-E- -N-LE7
	Encoder cable NEBM		
	5	550318	NEBM-M12W8-E-5-N-S1G15
	10	550319	NEBM-M12W8-E-10-N-S1G15
	15	550320	NEBM-M12W8-E-15-N-S1G15
	X length ¹⁾	550321	NEBM-M12W8-E- -N-S1G15
Connection from interface housing to the motor controller in the control cabinet			
	Motor cable NEBM		
	15	571907	NEBM-M12G4-RS-15-N-LE4
	Encoder cable NEBM		
	15	571915	NEBM-M12G12-RS-15-N-S1G15
Connecting cable NEBU for rod loss detection or reference sensor of the rotary drive			
	5	541334	NEBU-M8G3-K-5-LE3
	10	541332	NEBU-M8G3-K-10-LE3
	15	575986	NEBU-M8G3-K-15-LE3


1) Max. 25 m

Parallel kinematic robots EXPT, tripod

Accessories

Ordering data			
	Description	Part No.	Type
Protective conduit MKG			
	2 m are required per axis	177589	MKG-23-PG-29
Tubing holder EAHM			
	For attaching the protective conduit	1574902	EAHM-E10-TH
Angle kit EAHM			
	For attaching the tubing holder to the connection block	2075203	EAHM-E10-AK
		2075842	EAHM-E10-AK-P8¹⁾

1) For the variant EXPT-...-P8

Ordering data			
	Description	Part No.	Type
Adapter kit EAHA			
	For suction gripper ESG- (retainer size 2)	1574224	EAHA-R2-M12P
	For suction gripper ESG- (retainer size 3 and 4)	1574227	EAHA-R2-M14P

Parallel kinematic robots EXPT, tripod

Accessories





FESTO

Adapter kit
DHAA, HAPG

Material:
Wrought aluminium alloy
Free of copper and PTFE
RoHS-compliant

Note

The kit includes the individual mounting interface as well as the necessary mounting material.

Gripper combinations with adapter kit		Download CAD Data → www.festo.com/us/cad	
Grippers	Size	Adapter kit	
		Part No.	Type
Parallel gripper			
	DHPS, standard		
	6	187566	HAPG-SD2-12
	10	184477	HAPG-SD2-1
	16	184478	HAPG-SD2-2
	HGPT-B, heavy-duty		
	16	564958	DHAA-G-Q5-12-B8-16
	20	564955	DHAA-G-Q5-16-B8-20
	25	537181	HAPG-SD2-25
	HGPL, heavy-duty with long stroke		
	14-40, 14-60, 14-80	537310	HAPG-SD2-31
	HGPC		
	12	542671	HAPG-SD2-41
	16	542668	HAPG-SD2-42
	HGPD, sealed		
	16	564958	DHAA-G-Q5-12-B8-16
20	564955	DHAA-G-Q5-16-B8-20	
25	537181	HAPG-SD2-25	
Three-point gripper			
	DHDS, standard		
	16	187567	HAPG-SD2-13
	HGDT, heavy-duty		
	25	542439	HAPG-SD2-32
Radial gripper			
	DHRS, standard		
	10	187566	HAPG-SD2-12
	16	184477	HAPG-SD2-1
	25	184478	HAPG-SD2-2
	HGRT, heavy-duty		
	16	1273999	DHAA-G-Q5-16-B11-16
	HGRC		
	12	542671	HAPG-SD2-41
	16	542668	HAPG-SD2-42
Angle gripper			
	DHWS, standard		
	10	187566	HAPG-SD2-12
	16	184477	HAPG-SD2-1
	25	184478	HAPG-SD2-2
	HGWC		
	12	542671	HAPG-SD2-41
16	542668	HAPG-SD2-42	

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalnepantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com