

Parallel grippers HGPP, precision


FESTO



Parallel grippers HGPP, precision

Key features

FESTO



At a glance

- Wide range of variants for greater flexibility:
 - Double-acting piston drive HGPP-....-A.
 - Compression springs for supporting or retaining gripper forces, or for use as a single-acting gripper with only one compressed air connection
 - High precision gripper jaw guide
 - Choice of gripping action
 - External gripping
 - Internal gripping
 - Multiple compressed air connections
 - Integrated sensing electronics
 - Adaptable proximity sensor via mounting bracket
 - Highly flexible thanks to versatile attachment, mounting and applications options
 - Drives
 - Externally adaptable gripper fingers
 - Guide plate
- 1

 Compression spring closes gripper jaws:
HGPP-....-G2
- 2

 Compression spring opens gripper jaws:
HGPP-....-G1
- 3

 Synchronisation element
- 4

 Backlash-free guide bearing



Note

Sizing software
Gripper selection
→ www.festo.com


Parallel grippers HGPP, precision

Features


FESTO

Versatile air connections and mounting options

Supply port direct at the front,
direct mounting from above




Supply port via adapter plate from underneath,
direct mounting from above



- 1 Parallel gripper
- 2 Compressed air connection, opening
- 3 Compressed air connection, closing
- 4 Mounting screws
- 5 Locating pins
- 6 O-rings
- 7 Plate (user-specific)


Range of applications (user-specific)

Attachment of external gripper fingers






- 1 Parallel gripper
- 2 Gripper finger
- 3 Mounting screws
- 4 Locating pins
- 5 Guide plate

Used as guide plate



Note

Grippers are not suitable for the following, or for similar applications:




Parallel grippers HGPP, precision

System example

FESTO

System product for handling and assembly technology




System elements and accessories		
	Brief description	➔ Page/Internet
1 Drives	Wide range of combination options within handling and assembly technology	drive
2 Gripper	Diverse variation options in handling and assembly technology	gripper
3 Adapter	For drive/drive and drive/gripper connections	adapter kit
4 Basic mounting components	Profiles and profile connections as well as profile/drive connections	basic component
5 Installation components	For achieving a clear-cut, safe layout of electrical cables and tubing	installation component
– Axes	Diverse possible combinations in handling and assembly technology	axes
– Motors	Servo and stepper motors, with or without gearing	motor

Parallel grippers HGPP, precision

Peripherals overview and type codes

FESTO

Peripherals overview



Accessories			
	Brief description		→ Page/Internet
1	Threaded pin	For mounting proximity sensors SMH-S1	–
2	Position sensor SMH-S1	Can be integrated in the gripper	14
3	Evaluation unit SMH-AE1	For proximity sensor SMH-S1, for sensing 3 positions	14
4	Proximity sensor SIES-Q5B	Can be assembled with mounting bracket HGPP-HWS-Q5	14
5	Mounting bracket HGPP-HWS-Q5	For mounting proximity sensors SIES-Q5B, comprising 1 bracket and 1 switch lug with mounting screws	15
–	Adapter kit HMSV, HAPG	Drive/gripper connections	16

Type codes


		HGPP	–	16	–	A	–	G1
Type								
HGPP	Parallel gripper							
Size								
Position sensing								
A	Via proximity sensor							
Gripping force backup								
G1	Opening							
G2	Closing							

Parallel grippers HGPP, precision

FESTO

Technical data

Function
Double-acting
HGPP-...-A



Single-acting or
with gripping force retention ...
... opening HGPP-...-G1



... closing HGPP-...-G2



Ø 10 ... 32 mm

4 ... 25 mm

www.festo.com
Wearing parts kits
➔ 14



General technical data						
Size	10	12	16	20	25	32
Design	Rack and pinion					
Mode of operation	Double-acting					
Gripper function	Parallel					
Number of gripper jaws	2					
Max. weight force per external gripper finger ¹⁾ [N]	< 0.5	< 1	< 1.5	< 2	< 2.5	< 3
Stroke per gripper jaws [mm]	2	2.5	5	7.5	10	12.5
Pneumatic connection	M3		M5			G1/8/M5 ²⁾
Repetition accuracy ³⁾ [mm]	< 0.02	< 0.015		< 0.01	< 0.02	
Max. interchangeability [mm]	0.2					
Max. gripper jaw backlash [mm]	0					
Max. gripper jaw angular lash [°]	0					
Max. operating frequency [Hz]	4					
Centring precision [mm]	< Ø 0.05					
Position sensing	For proximity sensing					
Type of mounting	With through-hole and locating pin					
	With female thread and locating pin					

1) Valid for unthrottled operation

2) Supply port on side G1/8; supply port on ground M5

3) End-position drift under constant conditions of use with 100 consecutive strokes in the direction of movement of the gripper jaws

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Operating and environmental conditions			
Min. operating pressure	HGPP-...-A	[bar]	2
	HGPP-...-G...		5
Max. operating pressure		[bar]	8
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]		
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)		
Ambient temperature ¹⁾		[°C]	+5 ... +60
Corrosion resistance class CRC ²⁾	2		

1) Note operating range of proximity sensors

2) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents

Parallel grippers HGPP, precision


Technical data

FESTO

Weights [g]						
Size	10	12	16	20	25	32
HGPP-...-A	126	172	315	604	884	1,408
HGPP-...-G1	127	173	316	611	910	1,438
HGPP-...-G2	127	173	317	615	898	1,427

Materials


Sectional view



Parallel gripper


1	Housing	Anodised aluminium
2	Gripper jaw	Nickel-plated aluminium
3	Cover cap	Polyacetate
4	Plug cap	Anodised aluminium
- Note on material		Free of copper, PTFE and silicone Conforms to RoHS

Gripping force [N] at 6 bar



Size	10	12	16	20	25	32
Gripping force per gripper jaw						
Opening	40	58	102	170	250	415
Closing	40	58	102	170	250	415
Total gripping force						
Opening	80	116	204	340	500	830
Closing	80	116	204	340	500	830

Characteristic load values at the gripper jaws



Indicated permissible forces and torques apply to a single gripper jaw. Static forces and torques relate to additional applied loads caused by the workpiece or external gripper fingers,

as well as forces which occur during handling. The zero co-ordinate line (gripper jaws point of rotation) must be taken into consideration for the calculation of torques. Additionally,

max. permissible forces which may be applied to the housing have been entered as well, which, for example, can be absorbed by a guide plate during pressing-in operations.


Size	10	12	16	20	25	32
Max. permissible force $F_{Z\text{Gripper jaws}}$ [N]	40	70	130	220	380	720
Max. permissible force $F_{ZHousing}$ [N]	200	400	600	800	1,000	1,200
Max. permissible torque M_x [Nm]	1.5	3	7	14	21	30
Max. permissible torque M_y [Nm]	1.5	3	7	14	21	30
Max. permissible torque M_z [Nm]	1.5	3	7	14	21	30

Parallel grippers HGPP, precision

Technical data

FESTO

Mass moment of inertia [kgm²x10⁻⁴]





Mass moment of inertia [kgm²x10⁻⁴]
for parallel grippers in relation to the
central axis, without load.

Size	10	12	16	20	25	32
HGPP-...-A	0.43	0.73	2.39	6.22	16.68	38.34
HGPP-...-G1	0.45	0.76	2.58	6.71	17.45	39.21
HGPP-...-G2	0.43	0.74	2.45	6.27	16.85	38.63

Opening and closing times [ms] at 6 bar

without external gripper fingers

with external gripper fingers



The indicated opening and closing times [ms] have been measured at room temperature and 6 bar operating pressure with vertically mounted gripper and without external gripper fingers. Load is increased if external gripper fingers are attached. This means that kinetic energy is also increased, as this is determined by gripper finger weight and velocity. If permissible kinetic energy is exceeded, various parts of the gripper may be damaged. This occurs when the ap-

plied load reaches the end-position and the cushioning is only able to partially convert the kinetic energy into potential energy and heat energy. It thus becomes apparent that the indicated max. permissible applied load due to the external gripper fingers must be checked and maintained. The grippers must be throttled for greater applied loads. Opening and closing times must then be adjusted accordingly.

Size		10	12	16	20	25	32
Without external gripper fingers							
HGPP-...-A	Opening	22	27	40	44	64	76
	Closing	34	40	53	59	92	110
HGPP-...-G1	Opening	24	30	34	45	58	64
	Closing	95	70	70	92	164	173
HGPP-...-G2	Opening	26	37	57	62	105	103
	Closing	32	40	46	58	90	101
With external gripper fingers as a function of the weight force							
HGPP	1 N	100	–	–	–	–	–
	2 N	200	100	50	–	–	–
	3 N	300	200	100	50	100	–
	4 N	–	300	200	100	150	100
	5 N	–	–	300	200	200	150
	6 N	–	–	–	–	300	250


Parallel grippers HGPP, precision

Technical data


FESTO

Gripping force F_H as a function of operating pressure and the lever arm x


Gripping forces related to operating pressure and lever arm can be determined for the various sizes with the following graphs.




HGPP-10-A




HGPP-12-A




HGPP-16-A




HGPP-20-A



HGPP-25-A



HGPP-32-A




Parallel grippers HGPP, precision



Technical data

FESTO


Spring force F_F as a function of the gripper size and overall stroke length l



Gripper retention force, opening: the spring forces F_F of the parallel gripper HGPP-...-G1 can be determined from the following graphs.



Gripper retention force, closing: the spring forces F_F of the parallel gripper HGPP-...-G2 can be determined from the following graphs.



Determination of actual gripping forces for HGPP-...-G1 and HGPP-...-G2 depending upon the application

The parallel grippers with integrated spring can be used as:

- single-acting grippers
- grippers with supplementary gripping force and
- grippers with gripping force retention

In order to calculate available gripping forces F_{Gr} (per gripper jaw), gripping force (F_H) and spring force (F_F) must be combined accordingly.

Application

The resulting gripping force F_{Gr} , conditional on the application, depends on the gripping action (external/internal gripping) and the gripper design (with/without spring return). The spring force is supplemented in accordance with the design and gripping action.

Single-acting

- Gripping with spring force:
 $F_{Gr} = F_F$
- Gripping with pressure force:
 $F_{Gr} = F_H - F_F$

Supplementary gripping force

- Gripping with pressure and spring force:
 $F_{Gr} = F_H + F_F$

Gripping force retention

- Gripping with spring force:
 $F_{Gr} = F_F$


		Pressurised (in gripping action)	Unpressurised
HGPP-...-A	Internal gripping	$F_{Gr} = F_H$	$F_{Gr} = 0$
	External gripping	$F_{Gr} = F_H$	$F_{Gr} = 0$
HGPP-...-G1	Internal gripping	$F_{Gr} = F_H + F_F$	$F_{Gr} = F_F$
	External gripping	$F_{Gr} = F_H - F_F$	$F_{Gr} = 0$
HGPP-...-G2	Internal gripping	$F_{Gr} = F_H - F_F$	$F_{Gr} = 0$
	External gripping	$F_{Gr} = F_H + F_F$	$F_{Gr} = F_F$

Parallel grippers HGPP, precision

Technical data

FESTO

Gripping force F_H at 6 bar as a function of lever arm x and eccentricity y



Gripping forces at 6 bar dependent upon eccentric application of force and the maximum permissible off-centre point of force application can be determined for the various sizes using the following graphs.

Calculation example

Given:

Gripper HGPP-12-A

Lever arm $x = 20$ mm

Eccentricity $y = 22$ mm

To be found:


Gripping force at 6 bar

Procedure:


- Determine the intersection xy between lever arm x and eccentricity y in the graph for HGPP-12-A
- Draw an arc (with centre at origin) through intersection xy
- Determine the intersection between the arc and the X axis
- Read gripping force

Result:


Gripping force = approx. 55 N




HGPP-10-A




HGPP-12-A




HGPP-16-A




HGPP-20-A



HGPP-25-A



HGPP-32-A



Parallel grippers HGPP, precision


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

Mounting example for direct compressed air supply



- | | | | |
|---|-------------------------------------|--|---|
| 1 Compressed air connection, opening | 5 Gripper jaws closed | 9 O-ring for parallel grippers:
HGPP-10: \varnothing 5.5x1.5
HGPP-12: \varnothing 5.5x1.5
HGPP-16: \varnothing 8.13x1.78
HGPP-20: \varnothing 8.13x1.78
HGPP-25: \varnothing 8.13x1.78
HGPP-32: \varnothing 8.13x1.78
(Not included in scope of delivery) | 10 Set screw for mounting position sensor SMH-S1 |
| 2 Compressed air connection, closing | 6 Hole for sensor kit | | 11 Thread for securing the mounting bracket HGPP-HWS-Q5 |
| 3 Hole for locating pin
(Locating pins are not included in scope of delivery.) | 7 Parallel gripper | | 12 Supply ports on base sealed on delivery |
| 4 Gripper jaws open | 8 Adapter (e. g. customer-specific) | | |

Parallel grippers HGPP, precision

Technical data

FESTO

Size [mm]	B1 +0.3	B2 ±0.1	B3 ±0.05	B4 ±0.02 ¹⁾ ±0.1 ²⁾	B5 ±0.02	B6 ±0.1	B7 ±0.1	D1	D2 Ø +0.1
10	33	26	6.5	27	8	12.5	27	M4	3.3
12	38	29.5	6.5	30	8	12.5	30	M4	3.3
16	42	30.5	8.5	32	10	16	32	M4	3.3
20	48	36.5	10	40	12	20	40	M5	4.2
25	55	42	12	45	15	25	45	M6	5.1
32	62	45	14	52	18	30	52	M6	5.1

Size [mm]	D3 Ø H8	D4	D5 Ø H8	D6	D7	D8 Ø H11	EE	EE1	H1
10	3	M3	2	M2	M3	9	M3	M3	32.7 ±0.15
12	3	M3	2	M2	M3	9	M3	M3	37 +0.3/-0.1
16	3	M3	2.5	M2	M3	12.1	M5	M5	42.5 +0.4/-0.1
20	3	M4	3	M2	M3	12.1	M5	M5	55.5 +0.4/-0.1
25	5	M5	4	M2	M3	12.1	M5	M5	57.5 ±0.15
32	5	M6	5	M2	M4	12.1	M5	G ¹ / ₈	68.6 ±0.15

Size [mm]	H2 ±0.1	H3	H4 ±0.1	H5 ±0.02	H6 ±0.12	H7 -0.3	L1 ±0.5	L2 ±0.5	L3 ±0.25	L4 ±0.05
10	31.4	8.9 ±0.25	3.7	2	2.6	28.7	62	58	56	47.4
12	35.5	8.5 ±0.3	4.7	2	5	32.7	67	62	60	51.4
16	40.9	8.3 ±0.2	6.8	3	5	37.1	98	88	86	76
20	53.48	15.5 ±0.2	8	3	7	48.5	120	105	103	92
25	56	12.5 ±0.25	7.5	4	8	51	163	143	139.4	127.4
32	67	12.5 ±0.25	11	5	9	60.5	197.4	172.4	169.4	155.4

Size [mm]	L5 ±0.05	L6 ±0.1	L7	L8 ±0.1	L9 ±0.02	L10 ±0.05	L11 ±0.1	L12 ±0.05	T1
10	5	27	6	6	13.5	7.5	15	4	8
12	4	30	6	6.5	14	8.5	18	4	8
16	6.5	40	6	12	17.5	11.5	24	6.5	10
20	7.5	40	8	18	21	13.5	26	7.5	12
25	12	45	9	22	29.8	17	28	12	12
32	15	52	9	27	33.5	20	35	15	12

Size [mm]	T2	T3	T4	T5	T6	T7	T8	T9 +0.1	T10
10	14.85	6	8	5	4	6	3.8	1	3
12	16	6	7.5	5	4	6	5.5	1	3
16	19.5	7	8	6	4.5	6	5	1.3	4
20	28.5	7	10	8	7	8	6	1.3	7
25	27	10	10	8	8	10	6	1.3	8
32	34.5	10	10	10	10	10	8	1.3	8

1) For locating hole

2) For thread and through-holes

• Note: This product conforms to ISO 1179-1 and to ISO 228-1




Parallel grippers HGPP, precision

Ordering data and accessories

FESTO

Ordering data					
Size [mm]	Double-acting Without compression spring		Single-acting or with gripping force retention		
	Part No.	Type	Opening Part No.	Type	Closing Part No. Type
10	525 658	HGPP-10-A	525 659	HGPP-10-A-G1	525 660 HGPP-10-A-G2
12	187 867	HGPP-12-A	187 868	HGPP-12-A-G1	187 869 HGPP-12-A-G2
16	187 870	HGPP-16-A	187 871	HGPP-16-A-G1	187 872 HGPP-16-A-G2
20	187 873	HGPP-20-A	187 874	HGPP-20-A-G1	187 875 HGPP-20-A-G2
25	525 661	HGPP-25-A	525 662	HGPP-25-A-G1	525 663 HGPP-25-A-G2
32	525 664	HGPP-32-A	525 665	HGPP-32-A-G1	525 666 HGPP-32-A-G2

Ordering data – Wearing parts kits		
Size [mm]	Part No.	Type
10	673 172	HGPP-10
12	673 173	HGPP-12
16	673 174	HGPP-16
20	673 175	HGPP-20
25	673 176	HGPP-25
32	673 177	HGPP-32

Ordering data – Accessories				
	Size [mm]	Weight [g]	Part No.	Type
Position sensor SMH-S1			Technical data ➔ Internet: smh-s1	
	10, 12	20	189 040	SMH-S1-HGPP10/12
	16	20	189 041	SMH-S1-HGPP16
	20, 25	20	189 042	SMH-S1-HGPP20/25
	32	20	526 895	SMH-S1-HGPP32
Evaluation unit SMH-AE1			Technical data ➔ Internet: smh-ae1	
	10 ... 32	170	175 708	SMH-AE1-PS3-M12
		170	175 709	SMH-AE1-NS3-M12
Proximity sensor SIES-Q5B			Technical data ➔ Internet: sies	
	10 ... 32	22	178 291	SIES-Q5B-PS-K-L
		22	174 549	SIES-Q5B-PO-K-L
		22	178 290	SIES-Q5B-NS-K-L
		22	174 548	SIES-Q5B-NO-K-L

Parallel grippers HGPP, precision


Accessories

FESTO

Dimensions – Mounting bracket

HGPP-HWS-Q5

Download CAD data → www.festo.com



For size	B1	B2	H1	H2	H3	H4	H5	H6
[mm]								
10	8.7	0.5	35.5	14	0.5	1.2	7	2
12	8.7	0.5	35.5	14	0.5	1.2	7	2
16	8.5	0.5	35.4	16	0.5	1.2	8	3
20	8.5	0.5	36	20	0.5	2	10	3
25	9.5	0.55	46.3	24	1	3.7	12	4
32	9.5	0.55	55.5	28	1	4	14	5

For size	L1	L2	L3	L4	L5	L6	Weight	Part No.	Type
[mm]							[g]		
10	67.6	63.6	5.5	14	1.8	1.5	4.2	532 272	HGPP-HWS-Q5-1
12	73.6	68.6	5.5	14	1.8	1.5	5.6	532 273	HGPP-HWS-Q5-2
16	105.6	95.6	8.5	14	1.8	2	8.3	532 274	HGPP-HWS-Q5-3
20	126.8	111.8	8.5	14	2.4	2	11.4	532 275	HGPP-HWS-Q5-4
25	171	151	28	14	3	2	17.6	532 276	HGPP-HWS-Q5-5
32	206.6	181.6	28	14	3.6	2	24.6	532 277	HGPP-HWS-Q5-6

Parallel grippers HGPP, precision

Accessories

FESTO






Adapter kit
HAPG, HMSV, HMVA, DHAA

Material:
Wrought aluminium alloy
Free of copper and PTFE
RoHS-compliant



Note

The kit includes the individual mounting interface as well as the necessary mounting material.

Permissible drive/gripper combinations with adapter kit					Download CAD data ➔ www.festo.com		
Combination	Drive	Gripper			Adapter kit		
	Size	Size	Mounting option		CRC ¹⁾	Part No.	Type
							
DGSL/HGPP	DGSL	HGPP			HAPG		
	8, 10	10	■	■	2	529017	HAPG-57
	12, 16	10	■	■		529018	HAPG-58
	12, 16	12	■	■		191266	HAPG-48
	20, 25	12	■	■		191267	HAPG-49
	20, 25	16	■	■		191269	HAPG-51
	20, 25	20	■	■		191270	HAPG-52
SLT/HGPP	SLT	HGPP			HAPG		
	10	10	■	–	2	529017	HAPG-57
	16	10	■	–		529018	HAPG-58
	16	12	■	–		191266	HAPG-48
	20	12	■	–		191267	HAPG-49
	20	16	■	–		191268	HAPG-50
	25	16	■	–		191269	HAPG-51
	25	20	■	–		191270	HAPG-52
HMP/HGPP	HMP	HGPP			HAPG, HMSV		
	Direct mounting				2		
	16	12	–	■		191262	HAPG-44
	16	16	–	■		191263	HAPG-45
	20, 25, 32	16	–	■		191264	HAPG-46
	25, 32	20	–	■		191265	HAPG-47
	25, 32	25	–	■		529019	HAPG-59
	32	32	–	■		529020	HAPG-61
	Dovetail mounting				2		
	16	12	–	■		191262	HAPG-44
			–	■		177649	HMSV-3
	16	16	–	■		191263	HAPG-45
			–	■		177649	HMSV-3
	20, 25	16	–	■		191264	HAPG-46
			–	■		177653	HMSV-7
	25	20	–	■		191265	HAPG-47
			–	■		177653	HMSV-7
	25, 32	25	–	■		529019	HAPG-59
			–	■		177653	HMSV-7
	32	32	–	■		529020	HAPG-61
–			■	177653	HMSV-7		

1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.


Parallel grippers HGPP, precision





Accessories

FESTO

Adapter kit
HAPG, HMSV, HMVA, DHAA

Material:
Wrought aluminium alloy
Free of copper and PTFE
RoHS-compliant

 **Note**
The kit includes the individual mounting interface as well as the necessary mounting material.

Permissible drive/gripper combinations with adapter kit					Download CAD data ➔ www.festo.com		
Combination	Drive	Gripper			Adapter kit		
	Size	Size	Mounting option		CRC ¹⁾	Part No.	Type
							
DGP..., DGE-..., DGEA/HGPP	DG...	HGPP			HAPG, HMSV, HMVA		
	18 ²⁾ , 25 ³⁾	12	■	■	2	196788	HMVA-DLA18/25
						191262	HAPG-44
						177649	HMSV-3
	18 ²⁾ , 25 ³⁾	16	■	■		196788	HMVA-DLA18/25
						191263	HAPG-45
						177649	HMSV-3
	40 ³⁾	16	■	■		196790	HMVA-DLA40
						191264	HAPG-46
						177653	HMSV-7
	40 ³⁾	20	■	■		196790	HMVA-DLA40
						191265	HAPG-47
						177653	HMSV-7
	40 ³⁾	25	■	■	196790	HMVA-DLA40	
				529019	HAPG-59		
				177653	HMSV-7		
	40 ³⁾	32	■	■	196790	HMVA-DLA40	
				529020	HAPG-61		
				177653	HMSV-7		
DRQD/HGPP	DRQD	HGPP			HAPG		
	DRQD-...-FW				2		
	16 ⁴⁾ , 20 ⁴⁾	10	■	■		526023	HAPG-SD2-17
	16 ⁴⁾ , 20 ⁴⁾	12	■	■		191255	HAPG-SD2-14
	20 ⁴⁾ , 25 ⁵⁾	16	■	■		191256	HAPG-SD2-15
	25 ⁵⁾ , 32 ⁵⁾	20	■	■		191257	HAPG-SD2-16
	32 ⁵⁾ , 40, 50	25	■	■		526024	HAPG-SD2-18
	40, 50	32	■	■		526025	HAPG-SD2-19
	DRQD-...-ZW				2		
	16	12	■	■		191258	HAPG-40
	20	12	■	■		191259	HAPG-41
	25	16	■	■		191260	HAPG-42
		32	20	■	■	191261	HAPG-43

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 2) Only for DGEA-...
- 3) Only for DGE-.../DGP...
- 4) Possible in combination with DRQD-...-E422 (flanged shaft with energy through-feed).
- 5) Possible in combination with DRQD-...-E444 (flanged shaft with energy through-feed).

Parallel grippers HGPP, precision

Accessories

FESTO






Adapter kit
HAPG, HMSV, HMVA, DHAA

Material:
Wrought aluminium alloy
Free of copper and PTFE
RoHS-compliant



Note

The kit includes the individual mounting interface as well as the necessary mounting material.

Permissible drive/gripper combinations with adapter kit					Download CAD data → www.festo.com	
Combination	Drive	Gripper	Mounting option		Adapter kit	
	Size	Size			CRC ¹⁾	Part No. Type
						
DRRD/HGPP	DRRD	HGPP			DHAA	
	16	10	■	■	2	2157955 DHAA-G-Q11-16-B5-10
	16	12	■	■		2154048 DHAA-G-Q11-16-B5-12
	20	10	■	■		2158267 DHAA-G-Q11-20-B5-10
	20	12	■	■		2152457 DHAA-G-Q11-20-B5-12
	20	16	■	■		2152074 DHAA-G-Q11-20-B5-16
	25	16	■	■		1722274 DHAA-G-Q11-25-B5-16
	25	20	■	■		1722461 DHAA-G-Q11-25-B5-20
	32	20	■	■		2177999 DHAA-G-Q11-32-B5-20
	32	25	■	■		2180764 DHAA-G-Q11-32-B5-25
	35	25	■	■		2180954 DHAA-G-Q11-35-B5-25
	35, 40	32	■	■		2181855 DHAA-G-Q11-35/40-B5-32
HSP/HGPP	HSP	HGPP			HAPG	
	16	10	■	—	2	529017 HAPG-57
						540882 HAPG-71-B
	25	10	■	—		529017 HAPG-57
						540883 HAPG-72-B
	16	12	■	—		191900 HAPG-54
						540882 HAPG-71-B
	25	12	■	—		191900 HAPG-54
						540883 HAPG-72-B
	25	16	■	—		191901 HAPG-55
						540883 HAPG-72-B
HSW/HGPP	HSW	HGPP			HAPG	
	12, 16	10	■	—	2	529017 HAPG-57
						540882 HAPG-71-B
	16	12	■	—		191900 HAPG-54
						540882 HAPG-71-B
	16	16	■	—		191901 HAPG-55
						540882 HAPG-71-B

1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.


Parallel grippers HGPP, precision








Accessories

FESTO

Adapter kit
HAPG, HMSV, HMVA, DHAA

Material:
Wrought aluminium alloy
Free of copper and PTFE
RoHS-compliant

 **Note**
The kit includes the individual mounting interface as well as the necessary mounting material.

Permissible drive/gripper combinations with adapter kit					Download CAD data → www.festo.com		
Combination	Drive	Gripper			Adapter kit		
	Size	Size	Mounting option		CRC ¹⁾	Part No.	Type
							
DSM/HGPP	DSM	HGPP			HAPG		
	16	12	■	■	2	191258	HAPG-40
	25	12	■	■		191259	HAPG-41
	32	16	■	■		191260	HAPG-42
	40	20	■	■		191261	HAPG-43
DSL/HGPP	DSL	HGPP			HAPG		
	20	12	■	■	2	191258	HAPG-40
	25	12	■	■		191259	HAPG-41
	32	16	■	■		191260	HAPG-42
	40	20	■	■		191261	HAPG-43
EGSL/HGPP	EGSL	HGPP			HAPG, HMSV		
	35	10	■	■	2	1088262	HMSV-70
	45, 55	10	■	■		529018	HAPG-58
	45, 55	12	■	■		191266	HAPG-48
	75	12	■	■		191267	HAPG-49
	75	16	■	■		191269	HAPG-51
	35	10	■	■		529017	HAPG-57
EGSA/HGPP	EGSA	HGPP			HAPG, HMSV		
	50	10	■	■	2	529018	HAPG-58
						560017	HMSV-61
	50	12	■	■		191266	HAPG-48
						560017	HMSV-61
	60	12	■	■		191267	HAPG-49
						560018	HMSV-62
	60	16	■	■	191269	HAPG-51	
				560018	HMSV-62		
60	20	■	■	191270	HAPG-52		
				560018	HMSV-62		
ERMB/HGPP	ERMB	HGPP			HAPG		
	20	10	■	■	2	526023	HAPG-SD2-17
	20	12	■	■		191255	HAPG-SD2-14
	20, 25	16	■	■		191256	HAPG-SD2-15
	25, 32	20	■	■		191257	HAPG-SD2-16
	32	25	■	■		526024	HAPG-SD2-18

1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.


Parallel grippers HGPP, precision




Accessories

FESTO

Adapter kit
HAPG, HMSV, HMVA, DHAA

Material:
Wrought aluminium alloy
Free of copper and PTFE
RoHS-compliant

 **Note**
The kit includes the individual mounting interface as well as the necessary mounting material.

Permissible drive/gripper combinations with adapter kit					Download CAD data ➔ www.festo.com		
Combination	Drive	Gripper			Adapter kit		
	Size	Size	Mounting option		CRC ¹⁾	Part No.	Type
							
EHMB/HGPP	EHMB	HGPP			HAPG		
	20	20	■	■	2	191257	HAPG-SD2-16
	20, 25, 32	25	■	■		526024	HAPG-SD2-18
	25, 32	32	■	■		526025	HAPG-SD2-19

1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com