

Valve terminals MPA-L


FESTO



Valve terminals MPA-L

Key features

FESTO



Innovative

- Compact, high-performance valves in a sturdy metal housing
- Flow rates up to 870 l/min
- Wide range of electrical connection options for multi-pin plug: Sub-D, flat cable or terminal strip
- Connection to the electrical peripherals CPX with a wide range of communication options
- I-Port/IO-Link interface
- Freely configurable push-in connectors

Versatile

- Modular system offering a range of configuration options
- Freely extendable system with individual sub-bases and modular tie rods
- Up to 32 solenoid coils
- Conversions and extensions possible at a later date
- Air supply can be extended by additional pressure zones via supply modules
- Wide range of pressures –0.9 ... 10 bar
- Wide range of valve functions

Reliable


- High output reserves thanks to large pneumatic cross sections and venting with high flow rates
- Resilient thanks to high mechanical rigidity
- Lightweight and low-cost polymer components
- Fast troubleshooting thanks to LEDs on the valves
- Easy to service thanks to replaceable valves and electronic modules
- Manual override either non-detenting, detenting or secured against unauthorised activation (covered)
- Durable thanks to tried-and-tested piston spool valves

Easy to assemble

- Fast and reliable in-house assembly using individual components or delivered as a ready-to-install and tested unit
- Lower selection, ordering, installation and commissioning costs
- Secure mounting on wall or H-rail

Valve terminals MPA-L

Key features



Equipment options

Valve functions

- | | | | |
|--|--|---|--|
| <ul style="list-style-type: none"> • 5/2-way valve, single solenoid • 5/2-way valve, double solenoid • 2x 3/2-way valve, normally open • 2x 3/2-way valve, normally closed • 2x 3/2-way valve, 1x normally open, 1x normally closed | <ul style="list-style-type: none"> • 5/3-way valve, mid-position pressurised • 5/3-way valve, mid-position closed • 5/3-way valve, mid-position exhausted • 2x 2/2-way valve, 1x normally closed, 1x normally closed, reversible | <ul style="list-style-type: none"> • 2x 2/2-way valve, normally closed • 1x 3/2-way valve, normally closed, external compressed air supply • 1x 3/2-way valve, normally open, external compressed air supply • Manual pressure regulators | <p>All valves have the same compact dimensions with an overall length of 107 mm and a height of 55 mm.</p> |
|--|--|---|--|

Special features

- | | | | |
|---|---|---|--|
| <ul style="list-style-type: none"> • Max. 32 valve positions/max. 32 solenoid coils • Parallel, modular valve linking • Electrical interlinking with | <ul style="list-style-type: none"> • integrated holding current reduction • Any compressed air supply (max. 8 supply modules) | <ul style="list-style-type: none"> • Creation of pressure zones • Modular, individually extendable tie rods • Single valves or combinations of four valves | <ul style="list-style-type: none"> • Tubing size at each connection freely selectable |
|---|---|---|--|

Valve terminal selection

Valve terminal configurator

The appropriate MPA-L valve terminal can be chosen quickly and easily using the online catalogue. This includes a convenient valve terminal configurator, which makes it much simpler to order the right product.

The valve terminals are fully assembled according to your order specification and are individually tested. This reduces assembly and installation time to a minimum.

You order a valve terminal MPA-L using the order code.

Ordering system for MPA-L

→ Internet: mpal

Ordering system for CPX

→ Internet: cpx

Ordering system for CTEU

→ Internet: cteu

Online via: → www.festo.com

2D/3D CAD data


You can request the CAD data for a valve terminal you have configured. To do so, start the product search as described above. Go to the shopping basket and click on the CAD icon (compass). On the next page you can generate a 3D preview or request another data format of your choice by e-mail.

Valve terminals MPA-L

Key features

FESTO

Individual connection




Valves on individual sub-bases can also be used for actuators further away from the valve terminal. The valves are screwed to an individual sub-base made from die-cast aluminium.

The electrical connection is established using a standard 4-pin M8 plug (EN 60947-5-2).

Further information
→ Internet: vmpa1


Individual sub-base assembly



- 1 Mounting holes horizontal
- 2 Mounting holes vertical

The individual sub-base for wall mounting is designed for integration into a system or machine. It can be mounted horizontally or vertically.

Multi-pin plug connection



The signal flow from the controller to the valve terminal takes place via a pre-assembled or self-assembled multi-wire cable to the multi-pin plug connection, which substantially reduces installation time.

The valve terminal can be equipped with max. 32 solenoid coils. This corresponds to 2 to 32 valves.


Versions

- Sub-D connection
 - Pre-assembled multi-pin cable
 - Multi-pin cable for self-assembly
- Flat cable connection
- Terminal strip connection

Valve terminals MPA-L

Key features

Fieldbus connection via the CPX system



An integrated fieldbus node manages communication with a higher-order PLC. This enables a space-saving pneumatic and electronic solution. Valve terminals with fieldbus interfaces can be configured with up to 32 sub-bases.

The CPX terminal also enables the integration of digital and analogue electrical inputs and outputs, pressure sensors and controllers for pneumatic or electric positioning axes.


A detailed description of the extensive functionality can be found in the documentation for the CPX terminal

➔ Internet: [cpx](#)

Fieldbus protocols/CPX variants:

- PROFIBUS DP
- PROFINET
- INTERBUS
- DeviceNet
- CANopen
- CC-Link
- EtherNet/IP
- Front End Controller Remote I/O
- Modbus/TCP
- EtherCAT

Control block connection via the CPX system




Controllers integrated in the Festo valve terminals enable the construction of stand-alone control units to IP65, without control cabinets.

In the slave operating mode, these valve terminals can be used for intelligent preprocessing and are therefore ideal modules for designing decentralised intelligence.

In the master operating mode, terminal groups can be designed with many options and functions that can autonomously control a medium-sized machine/system.

Fieldbus connection via the CTEU system



Communication with a higher-level PLC is managed by a fieldbus node mounted directly on the I-Port interface. Valve terminals with an I-Port interface can be configured with up to 32 sub-bases.


A detailed description of the extensive functionality can be found in the documentation for the fieldbus modules CTEU/installation system CTCL

➔ Internet: [cteu](#)

Fieldbus protocols:

- PROFIBUS DP
- DeviceNet
- CANopen
- CC-Link
- EtherCAT

I-Port interface/IO-Link



I-Port/IO-Link consists of a central master and the devices with I-Port interface/IO-Link connected via special connecting cables. This permits a decentralised layout of the devices.

The connection type corresponds to a star topology.

In other words, only one module or valve terminal can be connected to each I-Port.

The I-Port interface from Festo is based on IO-Link and is compatible with IO-Link in certain areas.

As well as communication, the I-Port interfaces also handle the power supply for the connected devices. The maximum length of a string is 20 m.

Valve terminals MPA-L

Peripherals overview

Modular pneumatic components

The modular design of the MPA-L facilitates maximum flexibility right from the planning stage and offers maximum ease of servicing during operation.


The system consists of sub-bases and valves.

The sub-bases form the support system for the valves. They contain the connection ducts for supplying compressed air to and venting from the valve terminal as well as the working lines for the pneumatic drives for each valve.

The sub-bases are joined together via a tie rod system. This consists of a threaded rod, threaded sleeve and screw. The threaded rod/sleeve combination is selected as appropriate to the chosen number of individual sub-bases.

A valve terminal can be easily extended by adding individual sub-bases or supply modules. This is done by inserting suitable tie rod extenders between the threaded rod and sleeve.


This ensures that the valve terminal can be rapidly and reliably extended.



Note

The tie rod system for the valve terminal MPA-L consists of at least four sub-bases or two sub-bases and one supply module. Shorter valve terminals with two or more valve positions can be constructed without a sleeve.

Modular electrical peripherals



The mechanical connection between the CPX modules is established using tie rods. Two screws in the end plates are all that are needed to assemble the entire unit.

The tie rod ensures that the unit resists high mechanical loads and is therefore the "mechanical backbone" of the CPX terminal.

The open design allows interlinking blocks to be replaced in assembled state.

The tie rod extension kit allows an extra module to be added to the CPX terminal.

The input/output modules, connection blocks, fieldbus nodes or control block of the CPX system are mounted on the interlinking blocks using four screws and can be almost infinitely replaced or modified.

Valve terminals MPA-L

Peripherals overview


Individual sub-base

Ordering:

- Using individual part numbers

Individual sub-bases can be equipped with any valve (VMPA... of the corresponding width).

The electrical connection is established using a standard 4-pin M8 plug (EN 60947-5-2).



| Designation | Brief description | → Page/Internet |
|---|---|-----------------|
| 1 Solenoid valve | Width 10 mm, 14 mm, 20 mm | VMPA1 |
| 2 Manual override (MO) | Non-detenting/turning with detent, per solenoid coil | VMPA1 |
| 3 Cover cap | MO non-detenting only once cover cap fitted | VMPA1 |
| 4 Cover cap | MO blocked once cover cap fitted | VMPA1 |
| 5 Cover cap | MO detenting and can be operated without accessories once cover cap fitted | VMPA1 |
| 6 Sub-base | For individual valve VMPA... | VMPA1 |
| 7 Fittings and/or silencers | For working ports (2, 4) and air/exhaust ports (1, 3, 5) | VMPA1 |
| 8 Fittings, silencers or blanking plugs | For pilot air supply/pilot exhaust air (12/14, 82/84) and pressure compensation | VMPA1 |
| 9 Electrical connection M8 | 4-pin | VMPA1 |

Valve terminals MPA-L

Peripherals overview

Valve terminal – pneumatic components


The sub-bases are available individually with one valve position or with four valve positions.

The electrical interlinking modules are available for:

- 1 or 4 single solenoid valves
- 1 or 4 double solenoid valves

• Double solenoid valve positions can be fitted with any valve or a blanking plate.

• Single solenoid valve positions can only be fitted with single solenoid valves or a blanking plate.



Valve terminals MPA-L

Peripherals overview

FESTO

| Valve terminal – pneumatic components | | |
|---|---|-----------------|
| Designation | Brief description | → Page/Internet |
| 1 Plate | Exhaust plate as flat plate silencer | 61 |
| 2 Plate | Exhaust plate for ducted exhaust air | 61 |
| 3 Cartridge fitting | For supply and exhaust ports | 64 |
| 4 Cover cap for manual override | Conversion from detenting/non-detenting to non-detenting or detenting or covered | 60 |
| 5 Solenoid valve | Single solenoid | 50 |
| 6 Electrical interlinking module, 4-way | Electrical interlinking module for combination of four sub-bases, single solenoid/double solenoid | 53 |
| 7 Mounting bracket | Mounting bracket for wall mounting | 60 |
| 8 Regulator plate | Vertical stacking (pressure regulator, vertical pressure shut-off plate, vertical supply plate) | 51 |
| 9 Pressure gauge | Can be optionally mounted on a pressure regulator plate | 51 |
| 10 Right-hand end plate, low | End plate with pilot air selector, with ports 12/14, 82/84 | 62 |
| 11 Screw | Tie rod system, connects the sub-bases | 59 |
| 12 Right-hand end plate, high | End plate with pilot air selector, with ports 1, 3, 5, 12/14, 82/84 | 62 |
| 13 Inscription label | 6 x 10 mm | 60 |
| 14 Holder for inscription label | – | 60 |
| 15 Sub-base | Four individual sub-bases screwed together to form one unit | 53 |
| 16 Sleeve | Tie rod system, connects the sub-bases | 59 |
| 17 Tie rod extender | For subsequent modular extension of the valve terminal | 59 |
| 18 Tie rod | Threaded rod, clamps the sub-bases between the end plates | 59 |
| 19 Cartridge fitting | For working lines | 64 |
| 20 Sub-base, individual | Sub-base with one valve position | 53 |
| 21 Electrical interlinking module | Electrical interlinking module for single sub-base, single solenoid/double solenoid | 53 |
| 22 Clamp strap for cartridge fitting | – | – |
| 23 Supply module | For compressed air supply/exhaust air | 61 |
| 24 Electrical interlinking module | Electrical interlinking module for supply module, signals are passed through | 53 |
| 25 Restrictor | Fixed restrictor for installation in duct 3 or 5 of the sub-base | 52 |
| 26 Retainer for restrictor | Required to install the fixed restrictor | 52 |

Valve terminals MPA-L

Peripherals overview

FESTO

Valve terminal with multi-pin plug connection

Order code:

- 34P-...


MPA-L valve terminals with multi-pin plug connection can be expanded by up to 32 solenoid coils/valve positions.

The multi-pin plug connection is removable and designed as a 9, 25 or 44-pin Sub-D connection. The multi-pin plug connection can alternatively be ordered as a terminal strip (33-pin) or flat cable connection (40-pin).

The Sub-D multi-pin plug connection, 25 and 44-pin, is available in IP40 and IP67 or with multi-pin plug cover, without connecting cable, with a choice of cable outlet to the side or front.

Sub-D multi-pin plug connection, 25 and 44-pin, with multi-pin plug cover with pre-assembled cable:

- 2.5 m
- 5 m
- 10 m
- Variable, up to 30 m



| Designation | Brief description | → Page/Internet |
|-----------------------------|--|-----------------|
| 1 Multi-pin plug connection | Terminal strip, 33-pin, IP40 | 62 |
| 2 Multi-pin plug connection | For flat cable, 40-pin, IP40 | 62 |
| 3 Multi-pin plug connection | Sub-D, 25-pin | 62 |
| 4 Multi-pin plug connection | Sub-D, 9-pin, IP40 | 62 |
| 5 Connecting cable | With cover, pre-assembled, connection on side, IP67 | 63 |
| 6 Cover | For self-assembly, connection on side, IP67 | 63 |
| 7 Cover | For self-assembly, connection on front, IP67 | 63 |
| 8 Connecting cable | With cover, pre-assembled, connection on front, IP67 | 63 |

Valve terminals MPA-L

Peripherals overview

Valve terminal with fieldbus connection, control block (electrical peripherals CPX)

Order code:

- 34P-... for the pneumatic components
- 50E-... for the electrical peripherals

Valve terminals with CPX interface can be expanded by up to 32 solenoid coils/valve positions.

Up to 32 valve positions can be equipped in combination with single solenoid valves; the maximum number of valve positions is reduced to 16 if only double solenoid valves are used.


The maximum number of addresses is set in the range 4 ... 32 solenoid coils via a selector switch.

This enables extensions to be pre-assigned in a control program and called up by means of manual settings.

Each valve position can be equipped with any valve or a blanking plate. The rules for CPX apply to the equipment that can be used in combination with the electrical peripherals CPX.

In general:

- Digital inputs/outputs
- Analogue inputs/outputs
- Parameterisation of inputs and outputs
- Integrated multi-featured diagnostic system
- Preventive maintenance concepts



| Designation | Brief description | → Page/Internet |
|-----------------------|---|-----------------|
| 1 CPX modules | Fieldbus node, control block, input and output modules | cpx |
| 2 Left-hand end plate | Pneumatic interface for CPX terminal | 62 |
| 3 Inscription label | Large, for left-hand end plate/pneumatic interface for CPX terminal | - |
| 4 H-rail mounting | - | 60 |

Valve terminals MPA-L

Peripherals overview

Valve terminal with I-Port interface/IO-Link (and fieldbus node)


Order code:

- 34P-... for the pneumatic components
- CTEU-... for the fieldbus node

Valve terminals with I-Port interface/IO-Link can be expanded by up to 32 solenoid coils/valve positions.
Up to 32 valve positions can be equipped in combination with single solenoid valves.

The maximum number of valve positions is reduced to 16 if only double solenoid valves are used.

Each valve position can be equipped with any valve or a blanking plate.




| Designation | Brief description | → Page/Internet |
|-----------------------|---|-----------------|
| 1 Fieldbus node CTEU | Fieldbus node | cteu |
| 2 Plug | For I-Port interface/IO-Link | sea |
| 3 T-adaptor | For I-Port interface/IO-Link | fb-ta |
| 5 Connecting cable | Between two I-Port interfaces | nebv |
| 6 Electrical sub-base | With bus node for connecting two devices with I-Port interfaces | cteu |
| 7 H-rail mounting | For electrical sub-base | cteu |
| 8 Left-hand end plate | End plate with I-Port interface/IO-Link | 62 |

Valve terminals MPA-L

Key features – Pneumatic components

Sub-base valve



MPA-L offers a comprehensive range of valve functions. All valves are equipped with piston spool and patented sealing system that facilitates efficient sealing, a broad pressure range and long service life. They have a pneumatic pilot control for optimising performance.

Air is supplied by means of pilot air supply.
Sub-base valves can be quickly replaced since the tubing connectors remain on the sub-base.
This design is also particularly slim.

Irrespective of the valve function there are sub-base valves with one solenoid coil (single solenoid) or with two solenoid coils (double solenoid or two single solenoid valves in one housing).

Design

Valve replacement

The valves are attached to the sub-base using two screws, which means that they can be easily

replaced. The mechanical sturdiness of the sub-base guarantees good long-term sealing.

Extension

Blanking plates can be replaced by valves at a later date. The dimensions, mounting points and existing pneumatic installations remain

unchanged during this process. The valve code (e.g. M, J, N, NS, NU, etc.) is located on the front of the valve beneath the manual override.



Note

A filter must be installed upstream of valves operated in vacuum mode. This prevents any foreign matter in

the intake air getting into the valve (e.g. when operating a suction cup).

5/2-way valve

| Circuit symbol | Code | Description |
|----------------|----------------------------|--|
| | Position function 1-32: M | <ul style="list-style-type: none"> • Single solenoid • Pneumatic spring return • Reversible <ul style="list-style-type: none"> • Operating pressure $-0.9 \dots +10$ bar • Available in width 10 mm, 14 mm and 20 mm |
| | Position function 1-32: MS | <ul style="list-style-type: none"> • Single solenoid • Mechanical spring return • Reversible <ul style="list-style-type: none"> • Operating pressure $-0.9 \dots +8$ bar • Available in width 10 mm, 14 mm and 20 mm |
| | Position function 1-32: MU | <ul style="list-style-type: none"> • Single solenoid • Polymer poppet valve • Mechanical spring return <ul style="list-style-type: none"> • Reversible • Operating pressure $-0.9 \dots +10$ bar • Available in width 10 mm |
| | Position function 1-32: J | <ul style="list-style-type: none"> • Double solenoid • Reversible • Operating pressure $-0.9 \dots +10$ bar <ul style="list-style-type: none"> • Available in width 10 mm, 14 mm and 20 mm |

Valve terminals MPA-L

Key features – Pneumatic components



| 2x 3/2-way valve | | |
|------------------|----------------------------|--|
| Circuit symbol | Code | Description |
| | Position function 1-32: N | <ul style="list-style-type: none"> • Single solenoid • Normally open • Pneumatic spring return <ul style="list-style-type: none"> • Operating pressure 3 ... 10 bar • Available in width 10 mm, 14 mm and 20 mm |
| | Position function 1-32: NS | <ul style="list-style-type: none"> • Single solenoid • Normally open • Mechanical spring return • Reversible <ul style="list-style-type: none"> • Operating pressure -0.9 ... +8 bar • Available in width 10 mm, 14 mm and 20 mm |
| | Position function 1-32: NU | <ul style="list-style-type: none"> • Single solenoid • Polymer poppet valve • Normally open • Mechanical spring return <ul style="list-style-type: none"> • Reversible • Operating pressure -0.9 ... +10 bar • Available in width 10 mm |
| | Position function 1-32: K | <ul style="list-style-type: none"> • Single solenoid • Normally closed • Pneumatic spring return <ul style="list-style-type: none"> • Operating pressure 3 ... 10 bar • Available in width 10 mm, 14 mm and 20 mm |
| | Position function 1-32: KS | <ul style="list-style-type: none"> • Single solenoid • Normally closed • Mechanical spring return • Reversible <ul style="list-style-type: none"> • Operating pressure -0.9 ... +8 bar • Available in width 110 mm, 14 mm and 20 mm |
| | Position function 1-32: KU | <ul style="list-style-type: none"> • Single solenoid • Polymer poppet valve • Normally closed • Mechanical spring return <ul style="list-style-type: none"> • Reversible • Operating pressure -0.9 ... +10 bar • Available in width 10 mm |
| | Position function 1-32: H | <ul style="list-style-type: none"> • Single solenoid • Normal position <ul style="list-style-type: none"> - 1x closed - 1x open <ul style="list-style-type: none"> • Pneumatic spring return • Operating pressure 3 ... 10 bar • Available in width 10 mm, 14 mm and 20 mm |
| | Position function 1-32: HS | <ul style="list-style-type: none"> • Single solenoid • Normal position <ul style="list-style-type: none"> - 1x closed - 1x open • Mechanical spring return <ul style="list-style-type: none"> • Reversible • Operating pressure -0.9 ... +8 bar • Available in width 10 mm, 14 mm and 20 mm |
| | Position function 1-32: HU | <ul style="list-style-type: none"> • Single solenoid • Polymer poppet valve • Normal position <ul style="list-style-type: none"> - 1x closed - 1x open <ul style="list-style-type: none"> • Mechanical spring return • Reversible • Operating pressure -0.9 ... +10 bar • Available in width 10 mm |

Valve terminals MPA-L

Key features – Pneumatic components

| 5/3-way valve | | |
|----------------|---------------------------|--|
| Circuit symbol | Code | Description |
| | Position function 1-32: B | <ul style="list-style-type: none"> • Mid-position pressurised¹⁾ • Mechanical spring return • Reversible <ul style="list-style-type: none"> • Operating pressure –0.9 ... +10 bar • Available in width 10 mm, 14 mm and 20 mm |
| | Position function 1-32: G | <ul style="list-style-type: none"> • Mid-position closed¹⁾ • Mechanical spring return • Reversible <ul style="list-style-type: none"> • Operating pressure –0.9 ... +10 bar • Available in width 10 mm, 14 mm and 20 mm |
| | Position function 1-32: E | <ul style="list-style-type: none"> • Mid-position exhausted¹⁾ • Mechanical spring return • Reversible <ul style="list-style-type: none"> • Operating pressure –0.9 ... +10 bar • Available in width 10 mm, 14 mm and 20 mm |

1) If neither solenoid coil is energised, the valve moves to its mid-position by means of spring force.
If both coils are energised at the same time, the valve remains in the previously assumed switching position.

| 3/2-way valve | | |
|----------------|---------------------------|--|
| Circuit symbol | Code | Description |
| | Position function 1-32: W | <ul style="list-style-type: none"> • Single solenoid • Normally open • External compressed air supply • Pneumatic spring return • Reversible • Operating pressure –0.9 ... +10 bar <ul style="list-style-type: none"> • Available in width 10 mm, 14 mm and 20 mm • Compressed air (–0.9 ... +10 bar) supplied at working line 2 can be switched with both internal and external pilot air supply. |
| | Position function 1-32: X | <ul style="list-style-type: none"> • Single solenoid • Normally closed • External compressed air supply • Pneumatic spring return • Reversible • Operating pressure –0.9 ... +10 bar <ul style="list-style-type: none"> • Available in width 10 mm, 14 mm and 20 mm • Compressed air (–0.9 ... +10 bar) supplied at working line 4 can be switched with both internal and external pilot air supply. |


| 2x 2/2-way valve | | |
|------------------|----------------------------|--|
| Circuit symbol | Code | Description |
| | Position function 1-32: D | <ul style="list-style-type: none"> • Single solenoid • Normally closed • Pneumatic spring return <ul style="list-style-type: none"> • Operating pressure 3 ... 10 bar • Available in width 10 mm, 14 mm and 20 mm |
| | Position function 1-32: DS | <ul style="list-style-type: none"> • Single solenoid • Normally closed • Mechanical spring return • Reversible <ul style="list-style-type: none"> • Operating pressure –0.9 ... +8 bar • Available in width 10 mm, 14 mm and 20 mm |
| | Position function 1-32: I | <ul style="list-style-type: none"> • Single solenoid • 1x normally closed • 1x normally closed, reversible • Pneumatic spring return <ul style="list-style-type: none"> • Operating pressure 3 ... 10 bar • Vacuum at port 3/5 only • Available in width 10 mm, 14 mm and 20 mm |

Valve terminals MPA-L

Key features – Pneumatic components

FESTO


Blanking plate



Blanking plate (code L) without valve function, for reserving valve positions on a valve terminal.

Valves and blanking plates are attached to the sub-base using two screws.

Fixed restrictor



The fixed restrictor can be used to permanently set the flow rate when venting in ducts 3 and 5.

Mounting:

- Press the retainer as far as it will go into the exhaust openings on the sub-base
- Screw the fixed restrictor into the retainer
- Mount the valve on the sub-base

The restrictor cuts a thread into the retainer as it is screwed in. For that reason, the retainer should also be changed when a restrictor is repeatedly replaced.

The restrictor is available in seven different nominal sizes (0.3 ... 1.7 mm). The individual sizes are colour-coded to make them easy to distinguish.

Fixed restrictors enable, for example, the cylinder speed to be set to a predefined limit in response to known flow rate conditions.

They cannot be accessed during operation and are therefore protected against manipulation.

This is beneficial in the production of standard machines since the required speed can be determined once and the installation simply duplicated for further machines, saving time and costs for repeated commissioning.


-  - Note

The fixed restrictors are only available for valves and manifold sub-bases with a width of 10 mm.

Valve terminals MPA-L

Key features – Pneumatic components

Vertical stacking




Additional functions can be added to each valve position between the sub-base and the valve.

These functions are known as vertical stacking modules and enable special

functioning or control of an individual valve position.

Pressure regulator plate




An adjustable pressure regulator can be installed between the sub-base and the valve in order to control the force of the triggered actuator.

This pressure regulator maintains an essentially constant output pressure (secondary side) independent of pressure fluctuations (primary side) and air consumption.

Standard version:

- For supply pressure up to 6 bar or up to 10 bar
- Without pressure gauge (optional, rotatable)
- Adjusted using a screwdriver or regulator knob


Vertical pressure shut-off plate for width 10 mm



The vertical pressure shut-off plate can be used to hot swap individual valves without switching off the overall air supply.

The working pressure for the individual valve can be switched off manually via the vertical pressure shut-off plate using the actuating element.

Vertical pressure supply plate for width of 20 mm



This vertical pressure supply plate enables an individual valve to be supplied with individual operating pressure independently of the operating pressure of the valve terminal.

The exhaust and pilot air supply of the valve are still provided via the central connections of the valve terminal.

Valve terminals MPA-L

Key features – Pneumatic components



| Pressure regulator | | |
|--------------------|--|--|
| Circuit symbol | Code | Description |
| | Pressure regulator 1-32: PA Pressure regulator 1-32: PF | <ul style="list-style-type: none"> Regulates the pressure upstream of the valve in duct 1 Same regulated pressure at duct 2 and duct 4 Venting in the valve from duct 2 to duct 3 and from duct 4 to duct 5 <ul style="list-style-type: none"> Regulator not affected by venting Regulator can always be adjusted Available in width 10 mm and 20 mm |
| | Pressure regulator 1-32: PC Pressure regulator 1-32: PH | <ul style="list-style-type: none"> Regulates the pressure for duct 2 downstream of the valve Venting via the regulator from duct 2 to duct 3 Exhaust flow rate is restricted by the regulator <ul style="list-style-type: none"> Regulator can only be adjusted in switched state Available in width 10 mm and 20 mm |
| | Pressure regulator 1-32: PB Pressure regulator 1-32: PG | <ul style="list-style-type: none"> Regulates the pressure for duct 4 downstream of the valve Venting via the regulator from duct 4 to duct 5 Exhaust flow rate is restricted by the regulator <ul style="list-style-type: none"> Regulator can only be adjusted in switched state Available in width 10 mm and 20 mm |
| | Pressure regulator 1-32: PN Pressure regulator 1-32: PL | <ul style="list-style-type: none"> Splits the supply air in duct 1 and regulates the pressure upstream of the valve in duct 3 Valve is operated in reverse mode Venting in the valve from duct 2 to duct 1 <ul style="list-style-type: none"> Regulator not affected by venting Regulator can always be adjusted Available in width 20 mm |
| | Pressure regulator 1-32: PK Pressure regulator 1-32: PM | <ul style="list-style-type: none"> Splits the supply air in duct 1 and regulates the pressure upstream of the valve in duct 5 Valve is operated in reverse mode Venting in the valve from duct 4 to duct 1 <ul style="list-style-type: none"> Regulator not affected by venting Regulator can always be adjusted Available in width 20 mm |

| Vertical pressure shut-off plate | | |
|----------------------------------|-----------------------------|--|
| Circuit symbol | Code | Description |
| | Pressure regulator 1-32: PS | <ul style="list-style-type: none"> Allows the pressure in duct 1 and duct 12/14 to be switched off upstream of the valve Venting in the valve from duct 2 to duct 3 and from duct 4 to duct 5 <ul style="list-style-type: none"> Vertical pressure shut-off plate not affected by venting Operating pressure 3 ... 8 bar Available in width 10 mm |

Valve terminals MPA-L

Key features – Pneumatic components

| Vertical pressure supply plate | | |
|--------------------------------|-----------------------------|---|
| Circuit symbol | Code | Description |
| | Pressure regulator 1-32: PV | <ul style="list-style-type: none"> Enables separate supply of the pressure in duct 1 and upstream of the valve Operating pressure –0.9 ... +10 bar Available in width of 20 mm |

Compressed air supply and venting

| Supply module | Right-hand end plate | Compressed air supply and venting |
|---------------|----------------------|--|
| | | <p>The valve terminal MPA-L can be supplied with compressed air at one or more points via supply modules and/or the right-hand end plate. The generously sized pneumatic system enables good performance from all functional components, even with large-scale expansions.</p> <p>Venting (ducts 3 and 5) either takes place via silencers or ports for ducted exhaust air via the supply modules or the right-hand end plate. There are two types of supply module with venting:</p> <ul style="list-style-type: none"> Exhaust air 3/5 via flat plate silencer Exhaust air 3/5 ducted <p>Venting (ducts 3 and 5) can alternatively or additionally take place via the right-hand end plate. Ducts 3 and 5 are separate in the terminal and are only joined together in the supply module. The exhaust air from the pilot air (duct 82/84) is entirely separate from ducts 3 and 5.</p> |

Pilot air supply

| | |
|--|---|
| <p>The valve terminal MPA-L is supplied with pilot air exclusively via the right-hand end plate. The pilot air</p> | <p>supply can be selected at the pilot air selector on the end plate:</p> <ul style="list-style-type: none"> Internal (from duct 1) or External (from duct 12/14) |
|--|---|

Switching position for internal, marked "Int"

| | | |
|--|---|--|
| | <p>Internal pilot air supply can be selected if the supply pressure for the terminal is between 3 and 8 bar. In this case, the pilot air supply is branched by means of an internal</p> | <p>connection from duct 1 in the right-hand end plate. Port 12/14 on the right-hand end plate can be sealed using a blanking plug.</p> |
|--|---|--|

Switching position for external, marked "Ext"

| | | |
|--|--|---|
| | <p>If the supply pressure (at the right-hand end plate) is less than 3 bar or greater than 8 bar, then the valve terminal MPA-L must be operated with an external pilot air supply. The pilot air supply is then fed</p> | <p>via port 12/14 on the right-hand end plate. When using several pressure zones, the supply pressure in the pressure zone with the right-hand end plate is decisive.</p> |
|--|--|---|

Note

If a gradual pressure build-up in the system using a soft-start valve is chosen, an external pilot air supply should be connected so that the control pressure applied during switch-on is already very high.

Valve terminals MPA-L




Key features – Pneumatic components






| Compressed air supply and pilot air supply | | |
|---|---|---|
| Graphical illustration | Code | Notes |
| Right-hand end plate, with supply ports | | |
| | Right-hand end plate: D Pilot air: – | Internal pilot air supply <ul style="list-style-type: none"> • Pilot air is branched internally from port 1 in the right-hand end plate • Exhaust air 3/5 via right-hand end plate or supply module • Pilot exhaust air 82/84 via right-hand end plate • For operating pressure in the range 3 ... 8 bar |
| | Right-hand end plate: D Pilot air: E | External pilot air supply <ul style="list-style-type: none"> • Pilot air supply (3 ... 8 bar) is connected at the right-hand end plate at port 12/14 • Exhaust air 3/5 via right-hand end plate or supply module • Pilot exhaust air 82/84 via right-hand end plate • For operating pressure in the range –0.9 ... 10 bar (suitable for vacuum) |
| Right-hand end plate, without supply ports | | |
| | Right-hand end plate: – Pilot air: – | Internal pilot air supply <ul style="list-style-type: none"> • Pilot air is branched internally from port 1 in the right-hand end plate • Exhaust air 3/5 via supply module • Pilot exhaust air 82/84 via right-hand end plate • For operating pressure in the range 3 ... 8 bar |
| | Right-hand end plate: – Pilot air: E | External pilot air supply <ul style="list-style-type: none"> • Pilot air supply (3 ... 8 bar) is connected at the right-hand end plate at port 12/14 • Exhaust air 3/5 via supply module • Pilot exhaust air 82/84 via right-hand end plate • For operating pressure in the range –0.9 ... 10 bar (suitable for vacuum) |
| Supply module, flat plate silencer | | |
| | Type of module block 1-40: U Exhaust port: – | <ul style="list-style-type: none"> • Exhaust air 3/5 via flat plate silencer • Pilot exhaust air 82/84 via right-hand end plate • For operating pressure in the range –0.9 ... 10 bar (suitable for vacuum) |
| Supply module, ducted exhaust air | | |
| | Type of module block 1-40: U Exhaust port: UD, UE, UF, UM, UN, UP or UG | <ul style="list-style-type: none"> • Exhaust air 3/5 via supply module • Pilot exhaust air 82/84 via right-hand end plate • For operating pressure in the range –0.9 ... 10 bar (suitable for vacuum) |

Valve terminals MPA-L

Key features – Pneumatic components

| Supply module | | | | |
|---|---|------------|---|--|
| Illustration | Code | Type | Designation | Notes |
|  | Exhaust port: UD, UE, UF, UM, UN, UP or UG | VMPAL-EG | Exhaust plate for ducted exhaust air | Additional supply modules can be used for larger terminals or to create additional pressure zones. Supply modules can be configured at any point upstream or downstream of the sub-bases. Supply modules contain the following ports: <ul style="list-style-type: none"> Compressed air supply (duct 1) Exhaust air (duct 3/5) Depending on your order, the exhaust ducts are either ducted or vented via the flat plate silencer. |
|  | Exhaust port: – | VMPAL-EU | Flat plate silencer | |
|  | Type of module block 1-40: U | VMPAL-SP-0 | Supply module with electrical interlinking module | |


| Ports for supply and venting | | | | | |
|---|------------------------------|-------|-------------------|--------------------------------------|--|
| | Code | Port | | QS push-in fitting/cartridge fitting | |
| Right-hand end plate with supply ports 1, 3, 5 | | | | | |
|  | Right-hand end plate: D | 1 | Air/vacuum supply | Thread G $\frac{1}{4}$ | QS-G $\frac{1}{4}$, straight, for tubing O.D. \varnothing 8 mm, 10 mm, 12 mm, $\frac{5}{16}$ " , $\frac{3}{8}$ " , $\frac{1}{2}$ " |
| | | 3 | Exhaust air | Thread G $\frac{1}{4}$ | |
| | | 5 | Exhaust air | Thread G $\frac{1}{4}$ | |
| | | 12/14 | Pilot air supply | Thread M7 | QSM-M7, straight or angled, for tubing O.D. \varnothing 4 mm, 6 mm, $\frac{1}{4}$ " |
| | | 82/84 | Pilot exhaust air | Thread M7 | |
| Supply module | | | | | |
|  | Type of module block 1-40: U | 1 | Air/vacuum supply | Cartridge fitting | QSPKG20, straight, for tubing O.D. \varnothing 8 mm, 10 mm, 12 mm, $\frac{5}{16}$ " , $\frac{3}{8}$ " , $\frac{1}{2}$ " , adapter for thread G $\frac{1}{4}$ |
| | | 3/5 | Exhaust air | Flat plate silencer | – |
| | | | | Cartridge fitting | QSPKG20, straight, for tubing O.D. \varnothing 8 mm, 10 mm, 12 mm, $\frac{5}{16}$ " , $\frac{3}{8}$ " , $\frac{1}{2}$ " , adapter for thread G $\frac{1}{4}$ |
| | | 12/14 | Pilot air supply | – | – |
| | | 82/84 | Pilot exhaust air | – | – |
| Right-hand end plate without supply ports | | | | | |
|  | Right-hand end plate: – | 1 | Air/vacuum supply | – | – |
| | | 3 | Exhaust air | – | – |
| | | 5 | Exhaust air | – | – |
| | | 12/14 | Pilot air supply | Thread M7 | QSM-M7, straight or angled, for tubing O.D. \varnothing 4 mm, 6 mm, $\frac{1}{4}$ " |
| | | 82/84 | Pilot exhaust air | Thread M7 | |

Valve terminals MPA-L

Key features – Pneumatic components



Creating pressure zones and separating exhaust air



MPA-L offers a number of options for creating pressure zones if different working pressures are required. Up to nine pressure zones in total are possible.

Pressure zones are created by isolating the internal supply ducts in a special sub-base. Each pressure zone must have its own compressed air supply.

Compressed air can be supplied and vented via a supply module and/or the right-hand end plate.

The position of the supply modules and the sub-bases with pressure zone separation can be freely chosen with the valve terminal MPA-L.

The sub-bases with pressure zone separation are integrated in the terminal ex-works as per your order. They can be distinguished by their coding, even when the valve terminal is assembled. Duct separation always takes place to the right of the sub-base.

| Creating pressure zones | | Code | Notes |
|---|--------|---|---|
| Sub-bases with pressure zone separation | | | |
| Illustrated examples | Coding | | |
| | | Duct separation to the right of sub-base 1 - 40: – | <ul style="list-style-type: none"> No duct separation |
| | | Duct separation to the right of sub-base 1 - 40: T | <ul style="list-style-type: none"> Duct 1 separated VMPAL-...-T1 |
| | | Duct separation to the right of sub-base 1 - 40: TR | <ul style="list-style-type: none"> Duct 3/5 separated VMPAL-...-T35 |
| | | Duct separation to the right of sub-base 1 - 40: TS | <ul style="list-style-type: none"> Ducts 1 and 3/5 separated VMPAL-...-T135 |

Valve terminals MPA-L

Key features – Pneumatic components

Examples: Compressed air supply and pilot air supply


Internal pilot air supply, right-hand end plate without supply ports

The illustration opposite shows an example of the configuration and connection of the air supply with internal pilot air supply.

The exhaust air (duct 3/5) is discharged via supply modules.

The pilot exhaust air (duct 82/84) is discharged via the right-hand end plate.

Special sub-bases are used to create pressure zones.



External pilot air supply, right-hand end plate without supply ports


The illustration opposite shows an example of the configuration and connection of the compressed air supply with external pilot air supply.

Port 12/14 on the right-hand end plate is equipped with a fitting for this.

The exhaust air (duct 3/5) is discharged via supply modules.

The pilot exhaust air (duct 82/84) is discharged via the right-hand end plate.


Special sub-bases are used to create pressure zones.



Valve terminals MPA-L

Key features – Pneumatic components

Sub-base



MPA-L is based on a modular system consisting of sub-bases and valves. The sub-bases are connected together using tie rods and thus form the support system for the valves. They contain the connection ducts for supplying compressed air to and venting from the valve terminal as well as the working lines for the pneumatic drives for each valve.

The sub-bases are joined together via tie rods. The tie rod consists of a threaded rod, threaded sleeve and screw.

In principle, sub-bases have a modular structure. If this modularity is not required within a terminal, then four individual sub-bases can be combined with a 4-way electrical interlinking module to save costs.




The threaded rod/sleeve combination is selected as appropriate to the number and width of the individual sub-bases or sub-base combination. To add further blocks, simply loosen the tie rod and adapt with extenders. There are no restrictions on extensions; a tie rod could be made almost entirely from extenders.

Sub-base variants

| Illustration | Code | Type | Notes |
|--------------|-------------------------------|------------------|---|
| | - | VMPAL-AP-10 | <ul style="list-style-type: none"> Working lines 2, 4 on the sub-base Without electrical interlinking module |
| | | VMPAL-AP-14 | |
| | | VMPAL-AP-20 | |
| | | VMPAL-AP-...-QS | <ul style="list-style-type: none"> Working lines 2, 4 on the sub-base With electrical interlinking module |
| | | VMPAL-AP-...-T1 | <ul style="list-style-type: none"> Working lines 2, 4 on the sub-base With/without electrical interlinking module Duct separation in duct 1 |
| | | VMPAL-AP-...-T35 | <ul style="list-style-type: none"> Working lines 2, 4 on the sub-base Without electrical interlinking module Duct separation in ducts 3 and 5 |
| | Combination manifold block: Z | VMPAL-AP-4x10 | <ul style="list-style-type: none"> Working lines 2, 4 on the sub-base With/without electrical interlinking module No duct separation Four-valve unit, not suitable for pressure zone separation |

Valve terminals MPA-L

Key features – Pneumatic components

| Electrical interlinking module | | | | |
|---|------------------------------|---------------------|---|--|
| Illustration | Code | Type | No. of solenoid coils (valve positions) | Notes |
|  | Type of module block 1-40: A | VMPAL-EVAP-10-...-2 | 2 (1), double solenoid | Each solenoid coil must be assigned to a specific pin of the multi-pin plug for the valve to be actuated. Regardless of whether blanking plates or valves are used, valve positions occupy <ul style="list-style-type: none"> • one coil/address (single solenoid valves) • two coils/addresses (double solenoid valves) The electrical interlinking modules are colour-coded: <ul style="list-style-type: none"> • Single solenoid – grey • Double solenoid – black |
| | Type of module block 1-40: E | VMPAL-EVAP-14-...-2 | | |
| | Type of module block 1-40: B | VMPAL-EVAP-20-...-2 | | |
| | Type of module block 1-40: C | VMPAL-EVAP-10-...-1 | 1 (1), single solenoid | |
| | Type of module block 1-40: F | VMPAL-EVAP-14-...-1 | | |
| | Type of module block 1-40: D | VMPAL-EVAP-20-...-1 | | |
|  | Type of module block 1-40: A | VMPAL-EVAP-10-2-4 | 8 (4), double solenoid | Each solenoid coil must be assigned to a specific pin of the multi-pin plug for the valve to be actuated. Regardless of whether blanking plates or valves are used, valve positions occupy <ul style="list-style-type: none"> • one coil/address (single solenoid valves) • two coils/addresses (double solenoid valves) The electrical interlinking modules are colour-coded: <ul style="list-style-type: none"> • Single solenoid – grey • Double solenoid – black |
| | Type of module block 1-40: E | VMPAL-EVAP-14-2-4 | | |
| | Type of module block 1-40: C | VMPAL-EVAP-10-1-4 | 4 (4), single solenoid | |
| | Type of module block 1-40: F | VMPAL-EVAP-14-1-4 | | |
|  | Type of module block 1-40: U | VMPAL-EVAP-20-SP | – | Electrical interlinking module for power supply module |

Valve terminals MPA-L

Key features – Assembly

Valve terminal assembly

Sturdy terminal assembly thanks to:


- Four through-holes for wall mounting
- Additional mounting brackets
- H-rail mounting

 Note

If the terminal is subject to strong vibrations or shock loads, use additional mounting brackets of the type VMPAL-BD for wall mounting.

These should be attached to the valve terminal every 13 cm (one mounting bracket every 10 valve positions).


Wall mounting – Multi-pin plug connection



The MPA-L valve terminal is screwed onto the mounting surface using four M4 or M6 screws. The mounting holes are on the multi-pin plug connection

and on the right-hand end plate. Optional mounting brackets are also available.


Wall mounting – Fieldbus connection (CPX terminal)



The MPA-L valve terminal is screwed onto the mounting surface using four M4 and two M6 screws or using six M6 screws. The mounting holes are

on the left-hand and right-hand end plate and on the pneumatic interface. Optional mounting brackets are also available.

H-rail mounting



The MPA-L valve terminal is attached to the H-rail (see arrow A). The terminal is then swivelled onto the H-rail and secured in place with the clamping component (see arrow B).

The following MPA-L mounting kit is required for H-rail mounting of the valve terminal:

- With multi-pin plug connection: CPX-CPA-BG-NRH
- With fieldbus connection (CPX terminal): VMPAF-FB-BG-NRH

This enables mounting of the valve terminal on an H-rail to EN 60715.

 Note


The mounting kits (see above) only lock the valve terminal in horizontal mounting position.

Valve terminals MPA-L

Key features – Assembly

Tie rod

Design



Mode of operation

The tie rod for MPA-L consists of four parts:

- Threaded rod
- Tie rod extender
- Sleeve
- Screw

This enables valve terminals of any length to be created.

The tie rod and valve terminal are assembled in just four steps:

- Screw the threaded rods to the left-hand end plate
- Screw the sleeves to the threaded rods
- Push the sub-bases and supply modules onto the rod/sleeve combination
- Push on the right-hand end plate and secure with screws that engage into the sleeves





The tie rod enables subsequent extension of the valve terminal. This is done by loosening the tie rod screws and disassembling the relevant components. The additional sub-base or supply module is inserted at the required location. The previously disassembled components are then re-assembled.

To compensate for the change in length, the tie rod must be extended by the increase in length. This is done by screwing in extenders between the threaded rod and sleeve. There are suitable extenders for each sub-base, combination of four sub-bases and supply module.


Valve terminals MPA-L

Key features – Assembly


Tie rod – Components and design

| Tie rod (threaded rod) | Tie rod extender | Sleeve | Screw |
|---|--|---|---|
|  <p>The threaded rod is used to create a cost-optimised fixed-grid tie rod. The threaded rod is required with valve terminal lengths exceeding 42.45 mm, for example at least four sub-bases (10.7 mm each), since only the combination of a threaded rod and sleeve offers the optimum compensation of tolerances (by compressing the seals between the sub-bases).</p> |  <p>The valve terminal can be extended almost infinitely using tie rod extenders. The tie rod extenders are inserted between the threaded rod and sleeve and are available in appropriate lengths for sub-bases and supply modules.</p> |  <p>The primary purpose of the sleeve is to compensate tolerances that occur, for example, when the seals are compressed between the sub-bases during assembly. The sleeves come in different lengths, tailored to the use of a tie rod in a fixed grid as well as generally for the modular tie rods.</p> |  <p>The entire valve terminal is clamped via the tie rod using screws. Tolerances that occur, for example, when the seals are compressed between the sub-bases during assembly, are compensated by the interaction of the screws and sleeve.</p> |


Individual modular tie rod

| | |
|---|---|
|  | <p>Tie rods can be made entirely using tie rod extenders. The threaded rod and sleeve are required to compensate tolerances that occur, for example, when the seals are compressed between the sub-bases during assembly.</p> |
|---|---|


Fixed-grid tie rod with extension

| | |
|---|---|
|  | <p>The tie rod extenders are inserted between the threaded rod and sleeve. They are available in suitable lengths for sub-bases and supply modules.</p> |
|---|---|

Fixed-grid tie rod

| | |
|---|---|
|  | <p>The fixed-grid tie rod minimises assembly costs when assembling previously defined valve terminals. These valve terminals can be extended at any time.</p> <p>The threaded rod (and if applicable also the sleeve) must be replaced if the valve terminal length is reduced.</p> |
|---|---|

Short valve terminal

| | |
|---|--|
|  | <p>Valve terminals with a small number of valve positions are created by means of the following combinations:</p> <p>Width 10 mm</p> <ul style="list-style-type: none"> Valve terminals with two valve positions and without a supply module are connected solely using screws Valve terminals with three valve positions and without a supply module (or with one valve position and one supply module) are connected using a 10 mm tie rod extender and screw <p>Width 14 mm</p> <ul style="list-style-type: none"> Valve terminals with two valve positions and without a supply module are connected using a 10 mm tie rod extender and screw |
|---|--|

Valve terminals MPA-L

Key features – Assembly

| Ordering data – Fixed-grid tie rod | | | | |
|---|----------|---------------|----------|--------------|
| Reference length | Part No. | Type | Part No. | Type |
| L = 10.65 x V + 14.85 x W + 21.15 x Z + 21.15 x S | Tie rod | | Sleeve | |
| 42.3 ... 62.65 | 561116 | VMPAL-ZAS-5 | 561135 | VMPAL-ZAH-36 |
| 62.66 ... 72.30 | 561116 | VMPAL-ZAS-5 | 561136 | VMPAL-ZAH-46 |
| 72.31 ... 81.95 | 561116 | VMPAL-ZAS-5 | 561137 | VMPAL-ZAH-56 |
| 81.96 ... 91.60 | 561116 | VMPAL-ZAS-5 | 561138 | VMPAL-ZAH-66 |
| 91.61 ... 101.25 | 561117 | VMPAL-ZAS-45 | 561135 | VMPAL-ZAH-36 |
| 101.26 ... 110.90 | 561117 | VMPAL-ZAS-45 | 561136 | VMPAL-ZAH-46 |
| 110.91 ... 120.55 | 561117 | VMPAL-ZAS-45 | 561137 | VMPAL-ZAH-56 |
| 120.56 ... 130.20 | 561117 | VMPAL-ZAS-45 | 561138 | VMPAL-ZAH-66 |
| 130.21 ... 139.85 | 561118 | VMPAL-ZAS-85 | 561135 | VMPAL-ZAH-36 |
| 139.86 ... 149.50 | 561118 | VMPAL-ZAS-85 | 561136 | VMPAL-ZAH-46 |
| 149.51 ... 159.50 | 561118 | VMPAL-ZAS-85 | 561137 | VMPAL-ZAH-56 |
| 159.51 ... 169.15 | 561118 | VMPAL-ZAS-85 | 561138 | VMPAL-ZAH-66 |
| 169.16 ... 178.80 | 561119 | VMPAL-ZAS-125 | 561135 | VMPAL-ZAH-36 |
| 178.81 ... 188.45 | 561119 | VMPAL-ZAS-125 | 561136 | VMPAL-ZAH-46 |
| 188.46 ... 198.10 | 561119 | VMPAL-ZAS-125 | 561137 | VMPAL-ZAH-56 |
| 198.11 ... 207.75 | 561119 | VMPAL-ZAS-125 | 561138 | VMPAL-ZAH-66 |
| 207.76 ... 217.40 | 561120 | VMPAL-ZAS-165 | 561135 | VMPAL-ZAH-36 |
| 217.41 ... 227.05 | 561120 | VMPAL-ZAS-165 | 561136 | VMPAL-ZAH-46 |
| 227.06 ... 236.70 | 561120 | VMPAL-ZAS-165 | 561137 | VMPAL-ZAH-56 |
| 236.71 ... 246.35 | 561120 | VMPAL-ZAS-165 | 561138 | VMPAL-ZAH-66 |
| 246.36 ... 256.00 | 561121 | VMPAL-ZAS-205 | 561135 | VMPAL-ZAH-36 |
| 256.01 ... 266.00 | 561121 | VMPAL-ZAS-205 | 561136 | VMPAL-ZAH-46 |
| 266.01 ... 275.65 | 561121 | VMPAL-ZAS-205 | 561137 | VMPAL-ZAH-56 |
| 275.66 ... 285.30 | 561121 | VMPAL-ZAS-205 | 561138 | VMPAL-ZAH-66 |
| 285.31 ... 294.95 | 561122 | VMPAL-ZAS-245 | 561135 | VMPAL-ZAH-36 |
| 294.96 ... 304.60 | 561122 | VMPAL-ZAS-245 | 561136 | VMPAL-ZAH-46 |
| 304.61 ... 314.25 | 561122 | VMPAL-ZAS-245 | 561137 | VMPAL-ZAH-56 |
| 314.26 ... 323.90 | 561122 | VMPAL-ZAS-245 | 561138 | VMPAL-ZAH-66 |
| 323.91 ... 333.55 | 561123 | VMPAL-ZAS-285 | 561135 | VMPAL-ZAH-36 |
| 333.56 ... 343.20 | 561123 | VMPAL-ZAS-285 | 561136 | VMPAL-ZAH-46 |
| 343.21 ... 352.85 | 561123 | VMPAL-ZAS-285 | 561137 | VMPAL-ZAH-56 |
| 352.86 ... 362.50 | 561123 | VMPAL-ZAS-285 | 561138 | VMPAL-ZAH-66 |
| 362.51 ... 372.50 | 561124 | VMPAL-ZAS-325 | 561135 | VMPAL-ZAH-36 |
| 372.51 ... 382.50 | 561124 | VMPAL-ZAS-325 | 561136 | VMPAL-ZAH-46 |
| 382.51 ... 392.50 | 561124 | VMPAL-ZAS-325 | 561137 | VMPAL-ZAH-56 |
| 392.51 ... 402.50 | 561124 | VMPAL-ZAS-325 | 561138 | VMPAL-ZAH-66 |
| 402.51 ... 412.50 | 561125 | VMPAL-ZAS-365 | 561135 | VMPAL-ZAH-36 |
| 412.51 ... 422.50 | 561125 | VMPAL-ZAS-365 | 561136 | VMPAL-ZAH-46 |
| 422.51 ... 432.50 | 561125 | VMPAL-ZAS-365 | 561137 | VMPAL-ZAH-56 |
| 432.51 ... 442.50 | 561125 | VMPAL-ZAS-365 | 561138 | VMPAL-ZAH-66 |
| 442.51 ... 452.50 | 561126 | VMPAL-ZAS-405 | 561135 | VMPAL-ZAH-36 |
| 452.51 ... 462.50 | 561126 | VMPAL-ZAS-405 | 561136 | VMPAL-ZAH-46 |
| 462.51 ... 472.50 | 561126 | VMPAL-ZAS-405 | 561137 | VMPAL-ZAH-56 |
| 472.51 ... 482.50 | 561126 | VMPAL-ZAS-405 | 561138 | VMPAL-ZAH-66 |
| 482.51 ... 492.50 | 561127 | VMPAL-ZAS-445 | 561135 | VMPAL-ZAH-36 |
| 492.51 ... 502.50 | 561127 | VMPAL-ZAS-445 | 561136 | VMPAL-ZAH-46 |
| 502.51 ... 512.50 | 561127 | VMPAL-ZAS-445 | 561137 | VMPAL-ZAH-56 |
| 512.51 ... 522.50 | 561127 | VMPAL-ZAS-445 | 561138 | VMPAL-ZAH-66 |

- V Number of valve positions in width 10 mm
- W Number of valve positions in width 14 mm
- Z Number of valve positions in width 20 mm
- S Number of supply modules

Valve terminals MPA-L

FESTO

Key features – Assembly

| Ordering data – Fixed-grid tie rod | | | | |
|---|----------|---------------|----------|--------------|
| Reference length | Part No. | Type | Part No. | Type |
| $L = 10.65 \times V + 14.85 \times W + 21.15 \times Z + 21.15 \times S$ | | Tie rod | | Sleeve |
| 522.51 ... 532.50 | 561128 | VMPAL-ZAS-485 | 561135 | VMPAL-ZAH-36 |
| 532.51 ... 542.50 | 561128 | VMPAL-ZAS-485 | 561136 | VMPAL-ZAH-46 |
| 542.51 ... 552.50 | 561128 | VMPAL-ZAS-485 | 561137 | VMPAL-ZAH-56 |
| 552.51 ... 562.50 | 561128 | VMPAL-ZAS-485 | 561138 | VMPAL-ZAH-66 |
| 562.51 ... 572.50 | 561129 | VMPAL-ZAS-525 | 561135 | VMPAL-ZAH-36 |
| 572.51 ... 582.50 | 561129 | VMPAL-ZAS-525 | 561136 | VMPAL-ZAH-46 |
| 582.51 ... 592.50 | 561129 | VMPAL-ZAS-525 | 561137 | VMPAL-ZAH-56 |
| 592.51 ... 602.50 | 561129 | VMPAL-ZAS-525 | 561138 | VMPAL-ZAH-66 |
| 602.51 ... 612.50 | 561130 | VMPAL-ZAS-565 | 561135 | VMPAL-ZAH-36 |
| 612.51 ... 622.50 | 561130 | VMPAL-ZAS-565 | 561136 | VMPAL-ZAH-46 |
| 622.51 ... 632.50 | 561130 | VMPAL-ZAS-565 | 561137 | VMPAL-ZAH-56 |
| 632.51 ... 642.50 | 561130 | VMPAL-ZAS-565 | 561138 | VMPAL-ZAH-66 |
| 642.51 ... 652.50 | 561131 | VMPAL-ZAS-605 | 561135 | VMPAL-ZAH-36 |
| 652.51 ... 662.50 | 561131 | VMPAL-ZAS-605 | 561136 | VMPAL-ZAH-46 |
| 662.51 ... 672.50 | 561131 | VMPAL-ZAS-605 | 561137 | VMPAL-ZAH-56 |
| 672.51 ... 682.50 | 561131 | VMPAL-ZAS-605 | 561138 | VMPAL-ZAH-66 |
| 682.51 ... 692.50 | 561132 | VMPAL-ZAS-645 | 561135 | VMPAL-ZAH-36 |
| 692.51 ... 702.50 | 561132 | VMPAL-ZAS-645 | 561136 | VMPAL-ZAH-46 |
| 702.51 ... 712.50 | 561132 | VMPAL-ZAS-645 | 561137 | VMPAL-ZAH-56 |
| 712.51 ... 722.50 | 561132 | VMPAL-ZAS-645 | 561138 | VMPAL-ZAH-66 |
| 722.51 ... 732.50 | 561133 | VMPAL-ZAS-685 | 561135 | VMPAL-ZAH-36 |
| 732.51 ... 742.50 | 561133 | VMPAL-ZAS-685 | 561136 | VMPAL-ZAH-46 |
| 742.51 ... 752.50 | 561133 | VMPAL-ZAS-685 | 561137 | VMPAL-ZAH-56 |
| 752.51 ... 762.50 | 561133 | VMPAL-ZAS-685 | 561138 | VMPAL-ZAH-66 |
| 762.51 ... 772.50 | 561134 | VMPAL-ZAS-725 | 561135 | VMPAL-ZAH-36 |
| 772.51 ... 782.50 | 561134 | VMPAL-ZAS-725 | 561136 | VMPAL-ZAH-46 |
| 782.51 ... 792.50 | 561134 | VMPAL-ZAS-725 | 561137 | VMPAL-ZAH-56 |
| 792.51 ... 802.50 | 561134 | VMPAL-ZAS-725 | 561138 | VMPAL-ZAH-66 |
| 802.51 ... 812.50 | 561175 | VMPAL-ZAS-765 | 561135 | VMPAL-ZAH-36 |
| 812.51 ... 822.50 | 561175 | VMPAL-ZAS-765 | 561136 | VMPAL-ZAH-46 |
| 822.51 ... 832.50 | 561175 | VMPAL-ZAS-765 | 561137 | VMPAL-ZAH-56 |
| 832.51 ... 842.50 | 561175 | VMPAL-ZAS-765 | 561138 | VMPAL-ZAH-66 |
| 842.51 ... 852.50 | 561176 | VMPAL-ZAS-805 | 561135 | VMPAL-ZAH-36 |
| 852.51 ... 862.50 | 561176 | VMPAL-ZAS-805 | 561136 | VMPAL-ZAH-46 |

- V Number of valve positions in width 10 mm
- W Number of valve positions in width 14 mm
- Z Number of valve positions in width 20 mm
- S Number of supply modules

Valve terminals MPA-L

Key features – Display and operation

Display and operation

Signal status display

Each solenoid coil is allocated an LED that indicates its signal status.

- Indicator 12 shows the switching status of the coil for duct 2
- Indicator 14 shows the switching status of the coil for duct 4


Manual override

The manual override (MO) enables the valve to be actuated when not electrically activated or energised. The valve is switched by pushing the manual override.

Alternatives:

- A cover cap (code N, code y or as accessory) enables the manual override to be actuated by pressing it using an appropriate tool.
- A cover cap (code V) can be fitted over the manual override to prevent it from being accidentally actuated.

Pneumatic connection and control elements




- 1 Flat plate silencer, duct 3/5
- 2 Manual override (for each pilot solenoid coil, non-detenting or non-detenting/detenting)
- 3 Ducted exhaust air, duct 3/5
- 4 Ports 12/14 for external pilot air supply and 82/84 for pilot exhaust air in the right-hand end plate (depending on version also ducts 1, 3 and 5)
- 5 Supply port, duct 1
- 6 Working lines, ducts 2 and 4, for each valve position

Note

A valve actuated manually (by means of the manual override) cannot be reset electrically. Conversely, an electrically actuated valve cannot be reset using the manual override.


Manual override (MO)

MO with automatic return (non-detenting)



- 1 Press in the stem of the MO with a pointed object or screwdriver. Pilot valve switches and actuates the main valve.
- 2 Remove the pointed object or screwdriver. Spring force pushes the stem of the MO back. Pilot valve returns to its initial position and so too the single solenoid main valve (not with double solenoid valve code J).

MO set via turning (detenting)




- 1 Press in the stem of the MO with a pointed object or screwdriver until the valve switches and then turn the stem clockwise by 90° until the stop is reached. Valve remains switched.
- 2 Turn the stem anti-clockwise by 90° until the stop is reached and then remove the pointed object or screwdriver. Spring force pushes the stem of the MO back. Valve returns to its initial position (not with double solenoid valve code J).

Valve terminals MPA-L

Key features – Electrical components


Manual override (MO)

MO with cover cap, non-detenting




Manual override is actuated by pushing it with a pointed object or screwdriver and reset by spring force (detenting position prevented due to cover cap).

MO with cover cap, detenting without accessories, mounting




Clip cover onto pilot valve. The MO is then actuated by moving the slide on the cover cap.

MO with cover cap, detenting without accessories, actuation



Moving the slide on the cover cap in the direction of the arrow has the following effect:


- Slide locks into the end position
- Pilot valve switches and actuates the main valve



Moving the slide on the cover cap in the direction of the arrow has the following effect:

- Slide locks into the end position
- Spring force pushes the stem of the MO back.
- Pilot valve returns to its initial position and so too the single solenoid main valve (not with double solenoid valve code !)


Inscription system



A holder VMPAL-ST-AP-10 (Part No. 561109) with inscription labels (Part No. 18576, IBS-6x10) can be mounted on each sub-base for labelling the valves.

Large inscription labels can be attached to the pneumatic interface as an alternative or in addition to the smaller labels.

Electrical power as a result of current reduction




Each solenoid coil is protected with a spark arresting protective circuit as well as against polarity reversal. All valve types are additionally equipped with integrated current reduction.

MPA-L valves are supplied with operating voltage in the range 21.6 ... 26.4 V (24 V +/-10%).

Valve terminals MPA-L

Key features – Electrical components

Electrical connection – Left-hand end plate




The electrical connection for connecting the valves to a higher-level controller is located in the left-hand end plate. The different connection options can

be easily switched by replacing the left-hand end plate, while the pneumatic connections remain as they are.






The valves are switched by means of positive or negative logic (PNP or NPN). Mixed operation is not permitted.

Guidelines on addressing for valves/solenoid coils

- The numbering of the addresses goes from left to right in ascending consecutive order. The following applies to the individual valve positions: address x for coil 14 and address x+1 for coil 12.
- Each sub-base/electrical interlinking module occupies a defined number of addresses/pins:
 - For single solenoid valve: 1
 - For double solenoid valve: 2
 - For combination of four sub-bases for single solenoid valves: 4
 - For combination of four sub-bases for double solenoid valves: 8


 Note
If a single solenoid valve is assembled on a double solenoid valve position, the second address (for coil 12) is also occupied and cannot be used.


Left-hand end plate variants

| Illustration | Code | Type | Max. no. of addresses | Protection class | Notes |
|---|----------------------------|---------------------|-----------------------|------------------|--|
| Electrical multi-pin connection | | | | | |
|  | Electrical connection: MS1 | VMPAL-EPL-SD25-IP40 | 24 | IP40 | Electrical connection via Sub-D, 25-pin |
| | Electrical connection: MS2 | VMPAL-EPL-SD9-IP40 | 8 | IP40 | Electrical connection via Sub-D, 9-pin |
| | Electrical connection: MS6 | VMPAL-EPL-SD25 | 24 | IP65 | Electrical connection via Sub-D, 25-pin |
| | Electrical connection: MS8 | VMPAL-EPL-SD44 | 32 | IP65 | Electrical connection via Sub-D, 44-pin |
|  | Electrical connection: MF1 | VMPAL-EPL-FL40-IP40 | 32 | IP40 | Electrical connection via flat cable, 40-pin |
|  | Electrical connection: MC | VMPAL-EPL-KL33-IP40 | 32 | IP40 | Electrical connection via terminal strip, 33-pin |
| Fieldbus connection/CPX terminal | | | | | |
|  | Electrical connection: CX | VMPAL-EPL-CPX | 32 | IP67 | Electrical connection via CPX interlinking module |
| I-Port interface/IO-Link | | | | | |
|  | Electrical connection: LK | VMPAL-EPL-IPO32 | 32 | IP65 | Electrical connection via M12, 5 pin, IO-Link |
| | Electrical connection: PT | VMPAL-EPL-IPO32 | 32 | IP65 | Electrical connection via M12, 5 pin, I-Port interface |


Valve terminals MPA-L


Key features – Electrical components

| Pin allocation for electrical multi-pin plug connection – Sub-D plug, 9-pin | | | |
|---|-----|--------------|-------------------|
| | Pin | Address/coil | |
|  | 1 | 0 | 6 |
| | 2 | 1 | 7 |
| | 3 | 2 | 8 |
| | 4 | 3 | 9 |
| | 5 | 4 | 0 V ¹⁾ |
| | | | 6 |
| | | | 7 |
| | | | 8 |
| | | | 9 |
| | | | 0 V ¹⁾ |

 Note
 The drawing shows the view onto the pins of the Sub-D plug.


1) 0 V for positive switching control signals; connect 24 V for negative switching control signals; mixed operation is not permitted.


| Pin allocation for electrical multi-pin plug connection – Sub-D plug, 25-pin, connecting cable VMPAL-KM | | | | | | |
|---|-----|--------------|--|-----|-------------------|--|
| | Pin | Address/coil | Connecting cable wire colour ²⁾ | Pin | Address/coil | Connecting cable wire colour ²⁾ |
|  | 1 | 0 | WH | 14 | 13 | BN YE |
| | 2 | 1 | GN | 15 | 14 | GY WH |
| | 3 | 2 | YE | 16 | 15 | BN GY |
| | 4 | 3 | GY | 17 | 16 | WH PK |
| | 5 | 4 | PK | 18 | 17 | BN PK |
| | 6 | 5 | BU | 19 | 18 | BU WH |
| | 7 | 6 | RD | 20 | 19 | BN BU |
| | 8 | 7 | VT | 21 | 20 | RD WH |
| | 9 | 8 | GY PK | 22 | 21 | BN RD |
| | 10 | 9 | RD BU | 23 | 22 | BK WH |
| | 11 | 10 | GN WH | 24 | 23 | BN |
| | 12 | 11 | BN GN | 25 | 0 V ¹⁾ | BK |
| | 13 | 12 | YE WH | | | |

 Note
 The drawing shows the view onto the pins of the Sub-D plug.

1) 0 V for positive switching control signals; connect 24 V for negative switching control signals; mixed operation is not permitted.

2) To IEC 757

| Pin allocation for electrical multi-pin plug connection – Sub-D plug, 44-pin, connecting cable VMPAL-KM | | | | | | | | | |
|---|-----|--------------|--|-----|--------------|--|-----|-------------------|--|
| | Pin | Address/coil | Connecting cable wire colour ²⁾ | Pin | Address/coil | Connecting cable wire colour ²⁾ | Pin | Address/coil | Connecting cable wire colour ²⁾ |
|  | 1 | 0 | WH | 18 | 17 | BN PK | 35 | n.c. | n.c. |
| | 2 | 1 | GN | 19 | 18 | BU WH | 36 | n.c. | n.c. |
| | 3 | 2 | YE | 20 | 19 | BN BU | 37 | n.c. | n.c. |
| | 4 | 3 | GY | 21 | 20 | RD WH | 38 | n.c. | n.c. |
| | 5 | 4 | PK | 22 | 21 | BN RD | 39 | n.c. | n.c. |
| | 6 | 5 | BU | 23 | 22 | BK WH | 40 | n.c. | n.c. |
| | 7 | 6 | RD | 24 | 23 | BN | 41 | 0 V ¹⁾ | RD YE |
| | 8 | 7 | VT | 25 | 24 | BK BN | 42 | 0 V ¹⁾ | BK GN |
| | 9 | 8 | GY PK | 26 | 25 | GN GY | 43 | 0 V ¹⁾ | BK YE |
| | 10 | 9 | RD BU | 27 | 26 | YE GY | 44 | 0 V ¹⁾ | BK |
| | 11 | 10 | GN WH | 28 | 27 | GN PK | | | |
| | 12 | 11 | BN GN | 29 | 28 | YE PK | | | |
| | 13 | 12 | YE WH | 30 | 29 | GN BU | | | |
| | 14 | 13 | BN YE | 31 | 30 | YE BU | | | |
| | 15 | 14 | GY WH | 32 | 31 | RD GN | | | |
| | 16 | 15 | BN GY | 33 | n.c. | n.c. | | | |
| | 17 | 16 | WH PK | 34 | n.c. | n.c. | | | |

 Note
 The drawing shows the view onto the pins of the Sub-D plug.




1) 0 V for positive switching control signals; connect 24 V for negative switching control signals; mixed operation is not permitted.

2) To IEC 757

Valve terminals MPA-L

Key features – Electrical components

FESTO

| Electrical multi-pin connection – Ordering data | | | | | | |
|---|---|---|--|--------------|---------------|-----------------------------------|
| Designation | Code | Description | Connection | Cable length | Part No. | Type |
| Connecting cable for multi-pin plug connection with Sub-D plug socket | | | | | | |
|  | Connecting cable: CA | Cable outlet to front (only with electrical connection code: MS6) | 25-pin | 2.5 m | 560416 | VMPAL-KM-V-SD25-IP67-2,5 |
| | Connecting cable: CB | | | 5 m | 560417 | VMPAL-KM-V-SD25-IP67-5 |
| | Connecting cable: CC | | | 10 m | 560418 | VMPAL-KM-V-SD25-IP67-10 |
| | Connecting cable: – | | | Any | 562389 | VMPAL-KM-V-SD25-IP67-X |
| | Connecting cable: CQ | Cable outlet to front (only with electrical connection code: MS6) | 25-pin | 2.5 m | 560410 | VMPAL-KMSK-V-SD25-IP67-2,5 |
| | Connecting cable: CR | | | 5 m | 560411 | VMPAL-KMSK-V-SD25-IP67-5 |
| | Connecting cable: CS | | | 10 m | 560412 | VMPAL-KMSK-V-SD25-IP67-10 |
| | Connecting cable: – | | | Any | 562391 | VMPAL-KMSK-V-SD25-IP67-X |
| | Connecting cable: CJ | Cable outlet to front (only with electrical connection code: MS8) | 44-pin | 2.5 m | 560422 | VMPAL-KM-V-SD44-IP67-2,5 |
| | Connecting cable: CK | | | 5 m | 560423 | VMPAL-KM-V-SD44-IP67-5 |
| | Connecting cable: CL | | | 10 m | 560424 | VMPAL-KM-V-SD44-IP67-10 |
| | Connecting cable: – | | | Any | 562390 | VMPAL-KM-V-SD44-IP67-X |
| |  | Connecting cable: CD | Cable outlet to side (only with electrical connection code: MS6) | 25-pin | 2.5 m | 560419 |
| Connecting cable: CE | | 5 m | | | 560420 | VMPAL-KM-S-SD25-IP67-5 |
| Connecting cable: CH | | 10 m | | | 560421 | VMPAL-KM-S-SD25-IP67-10 |
| Connecting cable: – | | Any | | | 562392 | VMPAL-KM-S-SD25-IP67-X |
| Connecting cable: CT | | Cable outlet to side (only with electrical connection code: MS6) | 25-pin | 2.5 m | 560413 | VMPAL-KMSK-S-SD25-IP67-2,5 |
| Connecting cable: CU | | | | 5 m | 560414 | VMPAL-KMSK-S-SD25-IP67-5 |
| Connecting cable: CV | | | | 10 m | 560415 | VMPAL-KMSK-S-SD25-IP67-10 |
| Connecting cable: – | | | | Any | 562394 | VMPAL-KMSK-S-SD25-IP67-X |
| Connecting cable: CM | | Cable outlet to side (only with electrical connection code: MS8) | 44-pin | 2.5 m | 560425 | VMPAL-KM-S-SD44-IP67-2,5 |
| Connecting cable: CN | | | | 5 m | 560426 | VMPAL-KM-S-SD44-IP67-5 |
| Connecting cable: CP | | | | 10 m | 560427 | VMPAL-KM-S-SD44-IP67-10 |
| Connecting cable: – | | | | Any | 562393 | VMPAL-KM-S-SD44-IP67-X |
| Cover for multi-pin plug connection without connecting cable with Sub-D plug socket | | | | | | |
|  | Connecting cable: EZ | Cable outlet to side or front (only with electrical connection code: MS6) | 25-pin | – | 560428 | VMPAL-KM-SD25-IP67-0 |
| | Connecting cable: EY | Cable outlet to side or front (only with electrical connection code: MS8) | 44-pin | – | 560429 | VMPAL-KM-SD44-IP67-0 |

Valve terminals MPA-L

Key features – Electrical components



Pin allocation for electrical multi pin-plug connection – Flat cable, 40-pin

| | Pin | Address/coil | | Pin | Address/coil | | Pin | Address/coil |
|--|-----|--------------|--|-----|-------------------|--|---|-------------------|
| | 1 | 0 | | 18 | 17 | | 35 | 0 V ¹⁾ |
| | 2 | 1 | | 19 | 18 | | 36 | 0 V ¹⁾ |
| | 3 | 2 | | 20 | 19 | | 37 | 0 V ¹⁾ |
| | 4 | 3 | | 21 | 20 | | 38 | 0 V ¹⁾ |
| | 5 | 4 | | 22 | 21 | | 39 | 0 V ¹⁾ |
| | 6 | 5 | | 23 | 22 | | 40 | 0 V ¹⁾ |
| | 7 | 6 | | 24 | 23 | | <p>- - Note</p> <p>The drawing shows the view onto the pins of the flat cable plug. The flat cable connection is established using plug connectors, in accordance with DIN EN 60603-13:1998-09 (NECU-FCG40-K). → Internet: necu</p> | |
| | 8 | 7 | | 25 | 24 | | | |
| | 9 | 8 | | 26 | 25 | | | |
| | 10 | 9 | | 27 | 26 | | | |
| | 11 | 10 | | 28 | 27 | | | |
| | 12 | 11 | | 29 | 28 | | | |
| | 13 | 12 | | 30 | 29 | | | |
| | 14 | 13 | | 31 | 30 | | | |
| | 15 | 14 | | 32 | 31 | | | |
| | 16 | 15 | | 33 | 0 V ¹⁾ | | | |
| | 17 | 16 | | 34 | 0 V ¹⁾ | | | |

1) 0 V for positive switching control signals; connect 24 V for negative switching control signals; mixed operation is not permitted.

Pin allocation for electrical multi pin-plug connection – Terminal strip, 33-pin

| | Pin | Address/coil | | Pin | Address/coil | | Pin | Address/coil |
|--|-----|--------------|--|-----|--------------|--|---|-------------------|
| | 1 | 0 | | 16 | 15 | | 31 | 30 |
| | 2 | 1 | | 17 | 16 | | 32 | 31 |
| | 3 | 2 | | 18 | 17 | | 33 | 0 V ¹⁾ |
| | 4 | 3 | | 19 | 18 | | <p>- - Note</p> <p>The drawing shows the view onto the pins of the terminal strip. Cables with the following specifications can be connected:</p> <ul style="list-style-type: none"> • Cable cross section 0.08 ... 0.5 mm² • Insulation 5 ... 6 mm | |
| | 5 | 4 | | 20 | 19 | | | |
| | 6 | 5 | | 21 | 20 | | | |
| | 7 | 6 | | 22 | 21 | | | |
| | 8 | 7 | | 23 | 22 | | | |
| | 9 | 8 | | 24 | 23 | | | |
| | 10 | 9 | | 25 | 24 | | | |
| | 11 | 10 | | 26 | 25 | | | |
| | 12 | 11 | | 27 | 26 | | | |
| | 13 | 12 | | 28 | 27 | | | |
| | 14 | 13 | | 29 | 28 | | | |
| | 15 | 14 | | 30 | 29 | | | |

1) 0 V for positive switching control signals; connect 24 V for negative switching control signals; mixed operation is not permitted.

Valve terminals MPA-L

Key features – Electrical components

Fieldbus connection/CPX terminal

All functions and features of the electrical peripherals CPX are permitted in connection with the CPX interface.

This means:

- The valves and outputs are supplied via the system supply for the CPX terminal
- The valves can optionally be actuated or switched off separately from the outputs

The pneumatic interface (left-hand end plate) serves as an adapter between the two current feeds.

In the pneumatic interface, the serial signals from the CPX terminal are converted into parallel signals.

The number of addresses (solenoid coils that can be connected) is set via a selector (rotary switch) on the pneumatic interface to between 4 ... 32 solenoid coils. The default

setting on delivery provides for 32 addresses. This enables extensions to be pre-assigned in a control program and called up by means of manual settings.

After converting or extending the valve terminal, the number of output addresses occupied by the pneumatic components must be checked and if applicable adjusted.



Note

More information can be found at:
 → Internet: cpx

I-Port interface/IO-Link

The I-Port interface/IO-Link enables the valve terminal CPV to be connected to the following systems:

- I-Port master from Festo (CPX terminal, CECC)
- Fieldbus node CTEU from Festo

- IO-Link master
 The maximum distance between the I-Port/IO-Link master and valve terminal with I-Port interface/IO-Link is 20 m.

The 5-pin connecting cables contain the power supply for the valves, separate from this is the power supply for the internal valve terminal electronics and the control signals.



Note

More information can be found at:
 → Internet: cteu

Pin allocation I-Port interface/IO-Link

| | Pin | Designation |
|--|-----|--|
| | 1 | 24 V DC supply voltage for electronics and inputs |
| | 2 | 24 V DC load voltage supply for valves and outputs |
| | 3 | 0 V DC supply voltage for electronics and sensors |
| | 4 | Communication signal C/Q, data cable |
| | 5 | 0 V DC load voltage supply for valves and outputs |

Valve terminals MPA-L


Key features – Electrical components

FESTO

| Instructions for use | | |
|--|---|---|
| Equipment | Bio-oils | Mineral oils |
| <p>Operate system equipment with unlubricated compressed air if possible. Festo valves and cylinders are designed so that, if used as designated, they will not require additional lubrication and will still achieve a long service life. The quality of compressed air downstream of the compressor must correspond to that of unlubricated compressed air. If possible, do not operate all of your system equipment with lubricated compressed air. The lubricators should, where possible, always be installed directly upstream of the actuator used.</p> | <p>Unsuitable additional oil and too high an oil content in the compressed air reduce the service life of the valve terminal. Use Festo special oil OFSW-32 or the alternatives listed in the Festo catalogue (as specified in DIN 51524 HLP32; basic oil viscosity 32 CST at 40 °C).</p> | <p>When using bio-oils (oils which are based on synthetic or native ester, e.g. rapeseed oil methyl ester), the maximum residual oil content of 0.1 mg/m³ must not be exceeded (see ISO 8573-1 Class 2).</p> <p>When using mineral oils (e.g. HLP oils to DIN 51524, parts 1 to 3) or similar oils based on poly-alpha-olefins (PAO), the maximum residual oil content of 5 mg/m³ must not be exceeded (see ISO 8573-1 Class 4). A higher residual oil content irrespective of the compressor oil cannot be permitted, as the basic lubricant would be flushed out over time.</p> |


Valve terminals MPA-L

Technical data

-  - Flow rate
Up to 870 l/min

-  - Valve width
10 mm
14 mm
20 mm

-  - Voltage
24 V DC



| General technical data | | | | |
|--|--|----------------|---------|--------|
| Valve terminal design | Modular, valve sizes can be mixed | | | |
| Electrical actuation | Fieldbus | Multi-pin plug | IO-Link | I-Port |
| Type of actuation | Electrical | | | |
| Nominal operating voltage [V DC] | 24 | | | |
| Max. no. of valve positions | 32 | | | |
| Max. number of pressure zones | 9 | | | |
| Valve size [mm] | 10, 14, 20 | | | |
| Switching position display | LED | | | |
| Pilot air supply | Internal or external | | | |
| Lubrication | Life-time lubrication, PWIS-free (free of paint-wetting impairment substances) | | | |
| Type of mounting | Wall mounting On H-rail to EN 60715 | | | |
| Mounting position | Any (wall mounting) Horizontal only (H-rail) | | | |
| Manual override | Non-detenting, detenting | | | |
| Corrosion resistance class CRC ¹⁾ | 3 | | | |
| Note on materials | RoHS-compliant | | | |
| Degree of protection | IP65, IP67 | | | |

1) Corrosion resistance class 3 according to Festo standard 940 070
Components subject to high corrosion stress. Externally visible parts with primarily functional surface requirements which are in direct contact with the surrounding industrial environment or media such as solvents and cleaning agents.

| Operating and environmental conditions | |
|--|--|
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on operating/ pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Operating pressure [bar] | -0.9 ... +10 |
| Pilot pressure [bar] | 3 ... 8 |
| Ambient temperature [°C] | -5 ... +50 |
| Temperature of medium [°C] | -5 ... +50 |
| Storage temperature ¹⁾ [°C] | -20 ... +40 |
| Certification | RCM trademark |

1) Long-term storage

Valve terminals MPA-L

Technical data

| Technical data – Valve width 10 mm | | | | | | | | | | | | | | | | |
|--|-------------|--------------------|--------------|-----|------------------|-----|-----|-------------------|-----|-----|------------------|-----|----------|-----|--|--|
| Code for position function 1-32 | | M | J | N | K | H | B | G | E | X | W | D | I | | | |
| Design | | Piston spool valve | | | | | | | | | | | | | | |
| Sealing principle | | Soft | | | | | | | | | | | | | | |
| Non-overlapping | | Yes | | | | | | | | | | | | | | |
| Reset method | | Pneumatic spring | | | Pneumatic spring | | | Mechanical spring | | | Pneumatic spring | | | | | |
| Switching times | On | [ms] | 10 | 10 | 10 | 10 | 10 | 10 | 10 | 10 | 10 | 10 | 10 | 8 | | |
| | Off | [ms] | 20 | – | 20 | 20 | 20 | 35 | 35 | 35 | 20 | 20 | 20 | 20 | | |
| | Change-over | [ms] | – | 15 | – | – | – | 15 | 15 | 15 | – | – | – | – | | |
| Standard nominal flow rate | | [l/min] | 360 | 360 | 300 | 230 | 300 | 300 | 320 | 240 | 255 | 255 | 230 | 260 | | |
| Operating pressure | | [bar] | –0.9 ... +10 | | 3 ... 10 | | | –0.9 ... +10 | | | –0.9 ... +10 | | 3 ... 10 | | | |
| Pilot pressure | | [bar] | 3 ... 8 | | | | | | | | | | | | | |
| Max. tightening torque of valve mounting | | [Nm] | 0.25 | | | | | | | | | | | | | |
| Materials | | Die-cast aluminium | | | | | | | | | | | | | | |
| Product weight | | [g] | 49 | 56 | 56 | 56 | 56 | 56 | 56 | 56 | 49 | 49 | 56 | 56 | | |

| Technical data – Valve width 10 mm | | | | | | | | | | | | | |
|--|-------------|--------------------|-------------|-----|-----|-----|-----|---------------------------------|--------------|-----|-----|--|--|
| Code for position function 1-32 | | MS | NS | KS | HS | DS | MU | NU | KU | HU | | | |
| Design | | Piston spool valve | | | | | | Poppet valve with spring return | | | | | |
| Sealing principle | | Soft | | | | | | Soft | | | | | |
| Non-overlapping | | Yes | | | | | | No | | | | | |
| Reset method | | Mechanical spring | | | | | | Mechanical spring | | | | | |
| Switching times | On | [ms] | 10 | 14 | 14 | 14 | 14 | 10 | 8 | 8 | 8 | | |
| | Off | [ms] | 27 | 16 | 16 | 16 | 16 | 12 | 8 | 10 | 10 | | |
| | Change-over | [ms] | – | – | – | – | – | – | – | – | – | | |
| Standard nominal flow rate | | [l/min] | 360 | 300 | 230 | 300 | 230 | 190 | 190 | 160 | 190 | | |
| Operating pressure | | [bar] | –0.9 ... +8 | | | | | | –0.9 ... +10 | | | | |
| Pilot pressure | | [bar] | 3 ... 8 | | | | | | 4 ... 8 | | | | |
| Max. tightening torque of valve mounting | | [Nm] | 0.25 | | | | | | 0.25 | | | | |
| Materials | | Die-cast aluminium | | | | | | Reinforced PPA | | | | | |
| Product weight | | [g] | 56 | | | | | 35 | 42 | 42 | 42 | | |

| Technical data – Valve width 14 mm | | | | | | | | | | | | | | | | | | | | | |
|--|-------------|--------------------|--------------|-----|----------|-----|-------------------|--------------|-----|------------------|--------------|-----|----------|-------------------|-------------|-----|-----|-----|-----|--|--|
| Code for position function 1-32 | | M | J | N | K | H | B | G | E | X | W | D | I | MS | NS | KS | HS | DS | | | |
| Design | | Piston spool valve | | | | | | | | | | | | | | | | | | | |
| Sealing principle | | Soft | | | | | | | | | | | | | | | | | | | |
| Non-overlapping | | Yes | | | | | | | | | | | | | | | | | | | |
| Reset method | | Pneumatic spring | | | | | Mechanical spring | | | Pneumatic spring | | | | Mechanical spring | | | | | | | |
| Switching times | On | [ms] | 13 | 9 | 12 | 12 | 12 | 16 | 13 | 13 | 12 | 12 | 12 | 10 | 13 | 12 | 12 | 12 | 10 | | |
| | Off | [ms] | 30 | – | 38 | 38 | 38 | 50 | 52 | 50 | 20 | 20 | 30 | 28 | 30 | 23 | 23 | 23 | 25 | | |
| | Change-over | [ms] | – | 24 | – | – | – | 26 | 26 | 26 | – | – | – | – | – | – | – | – | – | | |
| Standard nominal flow rate | | [l/min] | 670 | 670 | 650 | 600 | 650 | 630 | 610 | 480 | 400 | 400 | 650 | 670 | 670 | 520 | 560 | 520 | 570 | | |
| Operating pressure | | [bar] | –0.9 ... +10 | | 3 ... 10 | | | –0.9 ... +10 | | | –0.9 ... +10 | | 3 ... 10 | | –0.9 ... +8 | | | | | | |
| Pilot pressure | | [bar] | 3 ... 8 | | | | | | | | | | | 3 ... 8 | | | | | | | |
| Max. tightening torque of valve mounting | | [Nm] | 0.65 | | | | | | | | | | | 0.65 | 0.25 | | | | | | |
| Materials | | Die-cast aluminium | | | | | | | | | | | | | | | | | | | |
| Product weight | | [g] | 77 | | | | | | | | | | | | | | | | | | |

Valve terminals MPA-L

Technical data

| Technical data – Valve width 20 mm | | | | | | | | | | | | | | | | | | | | | |
|--|-------------|--------------------|--------------|-----|-----|-----|-------------------|-----|-----|------------------|-----|-----|--------------|-------------------|----------|-----|-----|-------------|-----|--|--|
| Code for position function 1-32 | | M | J | N | K | H | B | G | E | X | W | D | I | MS | NS | KS | HS | DS | | | |
| Design | | Piston spool valve | | | | | | | | | | | | | | | | | | | |
| Sealing principle | | Soft | | | | | | | | | | | | | | | | | | | |
| Non-overlapping | | Yes | | | | | | | | | | | | | | | | | | | |
| Reset method | | Pneumatic spring | | | | | Mechanical spring | | | Pneumatic spring | | | | Mechanical spring | | | | | | | |
| Switching times | On | [ms] | 15 | 9 | 8 | 8 | 8 | 11 | 10 | 11 | 13 | 13 | 7 | 7 | 8 | 12 | 12 | 12 | 12 | | |
| | Off | [ms] | 28 | – | 28 | 28 | 28 | 46 | 40 | 47 | 22 | 22 | 25 | 23 | 36 | 25 | 25 | 25 | 25 | | |
| | Change-over | [ms] | – | 22 | – | – | – | 23 | 21 | 23 | – | – | – | – | – | – | – | – | – | | |
| Standard nominal flow rate | | [l/min] | 700 | 860 | 610 | 550 | 550 | 550 | 750 | 700 | 480 | 480 | 840 | 680 | 840 | 620 | 500 | 550 | 820 | | |
| Operating pressure | | [bar] | –0.9 ... +10 | | | | 3 ... 10 | | | –0.9 ... +10 | | | –0.9 ... +10 | | 3 ... 10 | | | –0.9 ... +8 | | | |
| Pilot pressure | | [bar] | 3 ... 8 | | | | | | | | | | | | | | | | | | |
| Max. tightening torque of valve mounting | | [Nm] | 0.65 | | | | | | | | | | | | | | | | | | |
| Materials | | Die-cast aluminium | | | | | | | | | | | | | | | | | | | |
| Product weight | | [g] | 100 | | | | | | | | | | | | | | | | | | |

| Safety characteristics | | | |
|--|--|-------------------|-------------------|
| | Valve width 10 mm | Valve width 14 mm | Valve width 20 mm |
| Note on forced switch on/off | Min. 1/week | | |
| CE marking (see declaration of conformity) | To EU EMC Directive ¹⁾ | | |
| Max. positive test pulse with 0 signal | [μs] | 400 | 400 |
| Max. negative test pulse with 1 signal | [μs] | 200 | 900 |
| Shock resistance | Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27 | | |
| Vibration resistance | Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6 | | |

1) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com/sp → User documentation.
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

Valve terminals MPA-L

Technical data


| Pneumatic connections | | |
|---|-------|--|
| Right-hand end plate | | |
| Supply | 1 | Thread G1/4 (QS-G1/4, straight, for tubing O.D. 8 mm, 10 mm, 12 mm, 5/16", 3/8", 1/2") |
| Exhaust port | 3 | Thread G1/4 (QS-G1/4, straight, for tubing O.D. 8 mm, 10 mm, 12 mm, 5/16", 3/8", 1/2") |
| | 5 | Thread G1/4 (QS-G1/4, straight, for tubing O.D. 8 mm, 10 mm, 12 mm, 5/16", 3/8", 1/2") |
| Pilot air supply | 12/14 | Thread M7 (QSM-M7, straight or angled, for tubing O.D. 4 mm, 6 mm, 1/4") |
| Pilot exhaust port | 82/84 | Thread M7 (QSM-M7, straight or angled, for tubing O.D. 4 mm, 6 mm, 1/4") |
| Power supply module | | |
| Supply | 1 | Cartridge fitting 20 mm (QSPKG20, straight, for tubing O.D. 8 mm, 10 mm, 12 mm, 5/16", 3/8", 1/2", adapter for thread G1/4), flat plate silencer |
| Exhaust port | 3/5 | Cartridge fitting 20 mm (QSPKG20, straight, for tubing O.D. 8 mm, 10 mm, 12 mm, 5/16", 3/8", 1/2", adapter for thread G1/4), flat plate silencer |
| Vertical pressure supply plate, width 20 mm | | |
| Supply | 1 | Thread G1/8 (QS-G1/8, straight, for tubing O.D. 8 mm, 10 mm, 5/16", 3/8") |
| Sub-base width 10 mm | | |
| Working ports | 2 | Cartridge fitting 10 mm (QSPKG10, straight or angled, for tubing O.D. 4 mm, 6 mm, 5/32", 1/4", adapter for thread M7) |
| | 4 | Cartridge fitting 10 mm (QSPKG10, straight or angled, for tubing O.D. 4 mm, 6 mm, 5/32", 1/4", adapter for thread M7) |
| Sub-base width 14 mm | | |
| Working ports | 2 | Cartridge fitting 14 mm (QSPKG14, straight or angled, for tubing O.D. 6 mm, 8 mm, 1/4", 5/16", adapter for thread G1/8) |
| | 4 | Cartridge fitting 14 mm (QSPKG14, straight or angled, for tubing O.D. 6 mm, 8 mm, 1/4", 5/16", adapter for thread G1/8) |
| Sub-base width 20 mm | | |
| Working ports | 2 | Cartridge fitting 18 mm (QSPKG18, straight or angled, for tubing O.D. 8 mm, 10 mm, 5/16", 3/8", adapter for thread G1/4) |
| | 4 | Cartridge fitting 18 mm (QSPKG18, straight or angled, for tubing O.D. 8 mm, 10 mm, 5/16", 3/8", adapter for thread G1/4) |

Valve terminals MPA-L


Technical data

Pilot pressure p2 as a function of working pressure p1 with external pilot air supply

For valves with code for position function 1-32: M, J, B, G, E, W, X




For valves with code for position function 1-32: N, K, H, D, I




Pilot pressure p2 as a function of working pressure p1 for valves with mechanical spring return


For valves in width 10 mm with code for position function 1-32: MS, NS, KS, HS, DS




For valves in width 14 mm with code for position function 1-32: MS, NS, KS, HS, DS



For valves in width 20 mm with code for position function 1-32: MS, NS, KS, HS, DS



For valves in width 10 mm with code for position function 1-32: MU, NU, KU, HU



Valve terminals MPA-L

Technical data

| Current consumption per solenoid coil at nominal voltage | | | | |
|--|------|-------|-------|-------|
| | | Width | | |
| | | 10 mm | 14 mm | 20 mm |
| Nominal pick-up current | [mA] | 50 | 50 | 110 |
| Nominal current with current reduction | [mA] | 10 | 10 | 23 |
| Time until current reduction | [ms] | 20 | 20 | 20 |

| Electrical data – MPA-L with electrical interface for CPX terminal | | |
|--|------|---------------|
| Intrinsic current consumption of valve terminal (internal electronics, without valves) | | |
| At 24 V $U_{EL/SEN}^{1)}$ | [mA] | Typically 13 |
| At 24 V $U_{val}^{2)}$ | [mA] | Typically 35 |
| Diagnostic message | | |
| Undervoltage $U_{OFF}^{3)}$ | [V] | 17.7 ... 17.8 |

- 1) Power supply for electronics and sensors
- 2) Load voltage supply for valves
- 3) Load voltage outside of function range

| Electrical data – MPA-L with I-Port interface/IO-Link | | |
|--|------|----|
| Intrinsic current consumption of valve terminal (internal electronics, without valves) | | |
| Operating voltage | [mA] | 30 |
| Load voltage | [mA] | 30 |

| Materials | |
|----------------------------------|--|
| Sub-base | PA |
| Power supply module | PPA |
| End plate | Die-cast aluminium, PA, PBT |
| Seals | NBR |
| Exhaust plate | PA |
| Flat plate silencer | PE |
| Electrical interlinking module | PBT, PA, copper alloy |
| Pressure regulator plate | PA |
| Vertical pressure shut-off plate | Reinforced PA, wrought aluminium alloy |
| Vertical pressure supply plate | Reinforced PA |

Valve terminals MPA-L

Technical data

FESTO

| Product weight | |
|---|--|
| | Approx. weight [g] |
| CPX module (complete) | Approx. 210 |
| Left-hand end plate, multi-pin plug, Sub-D, 44-pin | 130 |
| Left-hand end plate, I-Port interface/IO-Link | 170 |
| Power supply module with seal, electrical interlinking module | 51 |
| Right-hand end plate without supply ports | 105 |
| Right-hand end plate with supply ports | 160 |
| Valve | → 40 |
| Power supply module with seal, electrical interlinking module | 51 |
| Screw for tie rod | 3 |
| Threaded rods for tie rod, 5/45/85/125/165/205/245/285/325/365/405/445/485/525 mm | 2/11/20/29/38/47/54/65/72/80/89/98/109/118 |
| Sleeve for tie rod, 36/46/56/66 mm | 6/8/9/11 |
| Plate for ducted exhaust air/flat plate silencer | 36/40 |
| QSM-M7-4-I | 4 |
| QSM-M7-6-I | 5 |
| QS-G $\frac{1}{4}$ -8-I | 22 |
| QS-G $\frac{1}{4}$ -10-I | 23 |
| QSPKG10-3 | 1 |
| QSPKG10-4 | 1 |
| QSPKG10-6 | 2 |
| QSPKG20-8 | 6 |
| QSPKG20-10 | 9 |
| QSPKG20-12 | 12 |

| Product weight [g] | Product weight [g] | | |
|--|--------------------|-------------|-------------|
| | Width 10 mm | Width 14 mm | Width 20 mm |
| Black sub-base (with seal, fibre-optic cable) | 21 | 33 | 47 |
| Electrical interlinking module for one sub-base | 9 | 9 | 14 |
| Electrical interlinking module for combination of four sub-bases | 29 | – | – |
| Per vacant position L | 24 | 23 | – |
| Pressure regulator plate | 74 | – | 180 |
| Vertical pressure shut-off plate | 60 | – | – |
| Vertical pressure supply plate | – | – | 70 |

Valve terminals MPA-L


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

Valve terminal with multi-pin plug connection



| Type | L1 ¹⁾ | L2 ¹⁾ | L3 ¹⁾ | L4 ¹⁾ | L5 | L6 | L7 | L8 | L9 | L10 | L11 | L12 | L13 | L14 | L15 | L16 |
|-------|----------------------|------------------|------------------|------------------|----|------|------|------|------|------|-----|-----|-----|-----|-----|-----|
| MPA-L | 89.10 + L2 + L3 + L4 | m x 10.7 | n x 14.9 | o x 21.2 | 43 | 21.2 | 24.9 | 10.7 | 14.9 | 21.2 | 8.5 | 6.8 | 6.5 | 5.6 | 1.5 | 1 |

| Type | B1 | B2 | B3 | B4 | B5 | B6 | B7 | B8 | D1 | D2 | H1 | H2 | H3 | H4 | H5 | H6 | H7 |
|-------|-------|------|----|------|------|------|-----|-----|-----|-----|------|------|------|------|------|-----|------|
| MPA-L | 107.3 | 66.3 | 65 | 33.5 | 23.5 | 18.9 | 7.5 | 7.5 | 6.6 | 4.4 | 69.6 | 65.7 | 36.4 | 28.5 | 27.9 | 8.5 | 10.9 |

1) m, n, o = number of sub-bases/valve positions (m = width 10 mm, n = width 14 mm, o = width 20 mm)


Valve terminals MPA-L

Technical data

Dimensions

Download CAD data → www.festo.com

Valve terminal with fieldbus connection



- | | | | |
|-------------------------|-----------------------|--------------------------------------|-------------------|
| 1 Solenoid valve VMPA1 | 5 Power supply module | 9 Mounting holes | 11 CPX module |
| 2 Solenoid valve VMPA14 | 6 Working ports | 10 Pneumatic interface, CPX terminal | 12 Earthing screw |
| 3 Solenoid valve VMPA2 | 7 H-rail | | |
| 4 Manual override | 8 H-rail mounting | | |

| Type | L1 ¹⁾ | L2 ¹⁾ | L3 ¹⁾ | L4 ¹⁾ | L5 | L6 | L7 | L8 | L9 |
|-------|----------------------|------------------|------------------|------------------|-------|----|----|------|------|
| MPA-L | 170.9 + L2 + L3 + L4 | m x 10.7 | n x 14.9 | o x 21.2 | 141.8 | 50 | 40 | 21.2 | 28.9 |

| Type | L10 | L11 | L12 | L13 | L14 | L15 | L16 | L17 | L18 | L19 | L20 |
|-------|-----|-----|------|------|------|-----|-----|-----|-----|-----|-----|
| MPA-L | 24 | 30 | 10.7 | 14.9 | 21.2 | 8.5 | 6.8 | 5.6 | 6.5 | 1.5 | 1 |

| Type | B1 | B2 | B3 | B4 | B5 | B6 | B7 | B8 | B9 | B10 | B11 | D1 | D2 | D3 | H1 | H2 | H3 | H4 | H5 | H6 | H7 |
|-------|-----|-------|------|----|------|------|----|----|-----|-----|-----|-----|-----|----|------|------|----|------|------|------|-----|
| MPA-L | 124 | 107.3 | 66.3 | 65 | 33.5 | 23.5 | 15 | 13 | 7.5 | 5.3 | 5.5 | 6.6 | 4.4 | 7 | 69.6 | 65.7 | 52 | 39.8 | 28.5 | 25.8 | 8.5 |

1) m, n, o = number of sub-bases/valve positions (m = width 10 mm, n = width 14 mm, o = width 20 mm)

Valve terminals MPA-L


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

Valve terminal with I-Port interface/IO-Link



| Type | B1 | B2 | B3 | B4 | B5 | B6 | D1 | D2 | D3 | H1 | H2 | H3 | H4 | H5 | H6 | H7 |
|-------|-------|------|----|------|------|------|-----|-----|-----|------|------|------|------|------|-----|------|
| MPA-L | 107.3 | 66.3 | 65 | 33.5 | 23.5 | 18.9 | 6.6 | 6.4 | 4.5 | 69.6 | 65.7 | 36.4 | 28.5 | 27.9 | 8.5 | 10.9 |

| Type | L1 ¹⁾ | L2 ¹⁾ | L3 ¹⁾ | L4 ¹⁾ | L5 | L6 | L7 | L8 | L9 | L10 | L11 | L12 | L13 | L14 | L15 | L16 |
|-------|----------------------|------------------|------------------|------------------|------|------|------|------|------|------|-----|-----|-----|-----|-----|-----|
| MPA-L | 110.9 + L2 + L3 + L4 | m x 10.7 | n x 14.9 | o x 21.2 | 64.8 | 21.2 | 24.9 | 10.7 | 14.9 | 21.2 | 6.2 | 5.7 | 6.5 | 5.6 | 1.5 | 1 |

1) m, n, o = number of sub-bases/valve positions (m = width 10 mm, n = width 14 mm, o = width 20 mm)


Valve terminals MPA-L

Technical data


Dimensions – Cover for multi-pin plug connection

Download CAD data → www.festo.com

Cable outlet to front




Cable outlet to side



| Type | L1 | L2 | H1 | H2 | B1 | B2 | B3 |
|-----------------------|-------|----|------|----|------|----|----|
| Cable outlet to front | 108.3 | 27 | 44.4 | 14 | 34.5 | - | - |
| Cable outlet to side | 114.5 | - | 32.4 | 26 | 34.5 | 27 | 29 |

Valve terminal with vertical stacking (example: valve terminal with I-Port interface/IO-Link)





| Type | L1 | L2 | L3 | H1 |
|--------------|-------|-------|----|-------|
| VMPA...-B8-R | 175.1 | 120.7 | 15 | 138.7 |

Valve terminals MPA-L

Accessories






FESTO

| Ordering data | | | | |
|---|--|---|-----------------|-----------------|
| | Code | Valve function | Part No. | Type |
| Individual solenoid valve – Width 10 mm | | | | |
|  | 5/2-way valve | | | |
| | Position function 1-32: M | Single solenoid | 533342 | VMPA1-M1H-M-PI |
| | Position function 1-32: MS | Single solenoid, mechanical spring return | 571334 | VMPA1-M1H-MS-PI |
| | Position function 1-32: MU | Polymer poppet valve, single solenoid, mechanical spring return | 553113 | VMPA1-M1H-MU-PI |
| | Position function 1-32: J | Double solenoid | 533343 | VMPA1-M1H-J-PI |
| | 2x 3/2-way valve | | | |
| | Position function 1-32: N | Normally open | 533348 | VMPA1-M1H-N-PI |
| | Position function 1-32: NS | Normally open, mechanical spring return | 556839 | VMPA1-M1H-NS-PI |
| | Position function 1-32: NU | Polymer poppet valve, normally open, mechanical spring return | 553111 | VMPA1-M1H-NU-PI |
| | Position function 1-32: K | Normally closed | 533347 | VMPA1-M1H-K-PI |
| | Position function 1-32: KS | Normally closed, mechanical spring return | 556838 | VMPA1-M1H-KS-PI |
| | Position function 1-32: KU | Polymer poppet valve, normally closed, mechanical spring return | 553110 | VMPA1-M1H-KU-PI |
| | Position function 1-32: H | 1x normally open – 1x normally closed | 533349 | VMPA1-M1H-H-PI |
| | Position function 1-32: HS | 1x normally open – 1x normally closed, mechanical spring return | 556840 | VMPA1-M1H-HS-PI |
| | Position function 1-32: HU | Polymer poppet valve, 1x normally open – 1x normally closed, mechanical spring return | 553112 | VMPA1-M1H-HU-PI |
| | 5/3-way valve | | | |
| | Position function 1-32: B | Mid-position pressurised | 533344 | VMPA1-M1H-B-PI |
| | Position function 1-32: G | Mid-position closed | 533345 | VMPA1-M1H-G-PI |
| | Position function 1-32: E | Mid-position exhausted | 533346 | VMPA1-M1H-E-PI |
| | 1x 3/2-way valve | | | |
| Position function 1-32: W | Normally open, external compressed air supply | 540050 | VMPA1-M1H-W-PI | |
| Position function 1-32: X | Normally closed, external compressed air supply | 534415 | VMPA1-M1H-X-PI | |
| 2x 2/2-way valve | | | | |
| Position function 1-32: D | Normally closed | 533350 | VMPA1-M1H-D-PI | |
| Position function 1-32: DS | Normally closed, mechanical spring return | 556841 | VMPA1-M1H-DS-PI | |
| Position function 1-32: I | 1x normally closed 1x normally closed, reversible | 543605 | VMPA1-M1H-I-PI | |
| Vacant position – Width 10 mm | | | | |
|  | Position function 1-32: L | Blanking plate for one valve position in width 10 mm A self-adhesive label is supplied | 533351 | VMPA1-RP |

Valve terminals MPA-L




Accessories

FESTO

| Ordering data | | | | | | |
|---|-----------------------------|--|------------|---------------|-------------------------|---------------------------|
| | Code | Valve function | | | Part No. | Type |
| Vertical stacking modules – Width 10 mm | | | | | | |
|  | Pressure regulator 1-32: PF | Pressure regulator plate with fixed threaded connection M5 | For port 1 | 0.5 ... 5 | 564911 | VMPA1-B8-R1-M5-06 |
| | Pressure regulator 1-32: PA | | | 0.5 ... 8.5 | 564908 | VMPA1-B8-R1-M5-10 |
| | Pressure regulator 1-32: PH | | For port 2 | 2 ... 5 | 564912 | VMPA1-B8-R2-M5-06 |
| | Pressure regulator 1-32: PC | | | 2 ... 8.5 | 564909 | VMPA1-B8-R2-M5-10 |
| | Pressure regulator 1-32: PG | | For port 4 | 2 ... 5 | 564913 | VMPA1-B8-R3-M5-06 |
| | Pressure regulator 1-32: PB | | | 2 ... 8.5 | 564910 | VMPA1-B8-R3-M5-10 |
|  | Pressure regulator 1-32: PF | Pressure regulator plate with rotatable threaded connection M5 | For port 1 | 0.5 ... 5 | 549052 | VMPA1-B8-R1C2-C-06 |
| | Pressure regulator 1-32: PA | | | 0.5 ... 8.5 | 543339 | VMPA1-B8-R1C2-C-10 |
| | Pressure regulator 1-32: PH | | For port 2 | 2 ... 5 | 549053 | VMPA1-B8-R2C2-C-06 |
| | Pressure regulator 1-32: PC | | | 2 ... 8.5 | 543340 | VMPA1-B8-R2C2-C-10 |
| | Pressure regulator 1-32: PG | | For port 4 | 2 ... 5 | 549054 | VMPA1-B8-R3C2-C-06 |
| | Pressure regulator 1-32: PB | | | 2 ... 8.5 | 543341 | VMPA1-B8-R3C2-C-10 |
|  | Pressure regulator 1-32: PS | Vertical pressure shut-off plate For manually separating an individual valve from the compressed air supply for the valve terminal (ducts 1 and 12/14 pilot air supply), operating pressure 3 ... 8 bar | | | 567805 | VMPA1-HS |
|  | Pressure gauge 1-32: VE | Screw-in pressure gauge with thread M5 for pressure regulator plate with rotatable threaded connection | Unit bar | 132340 | MA-15-10-M5 | |
| | Pressure gauge 1-32: VD | | Unit psi | 132341 | MA-15-145-M5-PSI | |
|  | Pressure gauge 1-32: VC | Non-return valve with thread M5 for pressure regulator plate | | | 153291 | QSK-M5-4 |

Valve terminals MPA-L

Accessories







| Ordering data | | | | | | |
|---|-----------------------------------|---|-------------------|---------------|---------------------------|------------------|
| | Code | Description | | Part No. | Type | PU ¹⁾ |
| Fixed restrictor – Width 10 mm | | | | | | |
|  | Pneumatic connection 3, 1-40: V03 | Hollow bolt, for restricting the exhaust air | 3.5 ... 5.5 l/min | 572544 | VMPA1-FT-NW0.3-10 | 10 |
| | Pneumatic connection 5, 1-40: Q03 | | | | | |
| | Pneumatic connection 3, 1-40: V05 | | 9 ... 12 l/min | 572545 | VMPA1-FT-NW0.5-10 | 10 |
| | Pneumatic connection 5, 1-40: Q05 | | | | | |
| | Pneumatic connection 3, 1-40: V07 | | 18 ... 22 l/min | 572546 | VMPA1-FT-NW0.7-10 | 10 |
| | Pneumatic connection 5, 1-40: Q07 | | | | | |
| | Pneumatic connection 3, 1-40: V10 | | 36 ... 41 l/min | 572547 | VMPA1-FT-NW1.0-10 | 10 |
| | Pneumatic connection 5, 1-40: Q10 | | | | | |
| | Pneumatic connection 3, 1-40: V12 | | 52 ... 58 l/min | 572548 | VMPA1-FT-NW1.2-10 | 10 |
| | Pneumatic connection 5, 1-40: Q12 | | | | | |
| | Pneumatic connection 3, 1-40: V15 | | 81 ... 89 l/min | 572549 | VMPA1-FT-NW1.5-10 | 10 |
| | Pneumatic connection 5, 1-40: Q15 | | | | | |
| | Pneumatic connection 3, 1-40: V17 | | 105 ... 115 l/min | 572550 | VMPA1-FT-NW1.7-10 | 10 |
| | Pneumatic connection 5, 1-40: Q17 | | | | | |
| Restrictor set – Width 10 mm | | | | | | |
|  | – | Fixed restrictor, two of each size, two retainers and assembly tool | | 572543 | VMPA1-FT-NW0.3-1.7 | 14 |
| Retainer for fixed restrictor – Width 10 mm | | | | | | |
|  | – | Retainer for exhaust opening in the sub-base | | 572542 | VMPA1-FTI-10 | 10 |

1) Packaging unit quantity.

Valve terminals MPA-L



Accessories

FESTO

| Ordering data | | | | | | |
|---|---|---|--|-------|---------------|---------------------------------|
| | Code | Description | | | Part No. | Type |
| Sub-base – Width 10 mm | | | | | | |
|  | Duct separation to the right of sub-base 1-40: – | Single, without electrical interlinking module, without cartridge fitting | No duct separation | – | 554311 | VMPAL-AP-10 |
| | Duct separation to the right of sub-base 1-40: T | | Duct 1 separated | – | 554312 | VMPAL-AP-10-T1 |
| | Duct separation to the right of sub-base 1-40: TR | | Ducts 3, 5 separated | – | 554313 | VMPAL-AP-10-T35 |
| | Duct separation to the right of sub-base 1-40: TS | | Ducts 1 and 3, 5 separated | – | 554315 | VMPAL-AP-10-T135 |
|  | – | Single, with electrical interlinking module, single solenoid (for 1 solenoid coil), with cartridge fitting | No duct separation, tubing O.D. | 4 mm | 560994 | VMPAL-AP-10-QS4-1 |
| | | | | 6 mm | 560987 | VMPAL-AP-10-QS6-1 |
| | | | | 5/32" | 561005 | VMPAL-AP-10-QS5/32"-1 |
| | | | | 1/4" | 560999 | VMPAL-AP-10-QS1/4"-1 |
| | | | Duct 1 separated, tubing O.D. | 4 mm | 561017 | VMPAL-AP-10-QS4-1-T1 |
| | | | | 6 mm | 561011 | VMPAL-AP-10-QS6-1-T1 |
| | | | | 5/32" | 561029 | VMPAL-AP-10-QS5/32"-1-T1 |
| | | | | 1/4" | 561023 | VMPAL-AP-10-QS1/4"-1-T1 |
| | – | Single, with electrical interlinking module, double solenoid (for 2 solenoid coils), with cartridge fitting | No duct separation, tubing O.D. | 4 mm | 560988 | VMPAL-AP-10-QS4-2 |
| | | | | 6 mm | 560993 | VMPAL-AP-10-QS6-2 |
| | | | | 5/32" | 561006 | VMPAL-AP-10-QS5/32"-2 |
| | | | | 1/4" | 561000 | VMPAL-AP-10-QS1/4"-2 |
| | | | Duct 1 separated, tubing O.D. | 4 mm | 561018 | VMPAL-AP-10-QS4-2-T1 |
| | | | | 6 mm | 561012 | VMPAL-AP-10-QS6-2-T1 |
| | | | | 5/32" | 561030 | VMPAL-AP-10-QS5/32"-2-T1 |
| | | | | 1/4" | 561024 | VMPAL-AP-10-QS1/4"-2-T1 |
| Combination of four sub-bases – Width 10 mm | | | | | | |
|  | Combination manifold block: Z | Without electrical interlinking module, without cartridge fitting | – | – | 560981 | VMPAL-AP-4x10 |
|  | – | With electrical interlinking module, single solenoid (for 1 solenoid coil), with cartridge fitting | No duct separation, tubing O.D. | 4 mm | 561089 | VMPAL-AP-4X10-QS4-1 |
| | | | | 6 mm | 561083 | VMPAL-AP-4X10-QS6-1 |
| | | | | 5/32" | 561101 | VMPAL-AP-4X10-QS5/32"-1 |
| | | | | 1/4" | 561095 | VMPAL-AP-4X10-QS1/4"-1 |
| | – | With electrical interlinking module, double solenoid (for 2 solenoid coils), with cartridge fitting | No duct separation, tubing O.D. | 4 mm | 561090 | VMPAL-AP-4X10-QS4-2 |
| | | | | 6 mm | 561084 | VMPAL-AP-4X10-QS6-2 |
| | | | | 5/32" | 561102 | VMPAL-AP-4X10-QS5/32"-2 |
| | | | | 1/4" | 561096 | VMPAL-AP-4X10-QS1/4"-2 |
| Electrical interlinking module – Width 10 mm | | | | | | |
|  | Type of module block 1-40: C | For one sub-base (1 valve position) | Grey – single solenoid (1 solenoid coil) | | 560961 | VMPAL-EVAP-10-1 |
| | Type of module block 1-40: A | | Black – double solenoid (2 solenoid coils) | | 560962 | VMPAL-EVAP-10-2 |
|  | Type of module block 1-40: C | For combination of four sub-bases (4 valve positions) | Grey – single solenoid (4 solenoid coils) | | 560967 | VMPAL-EVAP-10-1-4 |
| | Type of module block 1-40: A | | Black – double solenoid (8 solenoid coils) | | 560968 | VMPAL-EVAP-10-2-4 |

Valve terminals MPA-L







Accessories

| Ordering data | | | | |
|---|--|---|------------------|------------------|
| | Code | Valve function | Part No. | Type |
| Individual solenoid valve – Width 14 mm | | | | |
|  | 5/2-way valve | | | |
| | Position function 1-32: M | Single solenoid | 573718 | VMPA14-M1H-M-PI |
| | Position function 1-32: MS | Single solenoid | 573974 | VMPA14-M1H-MS-PI |
| | Position function 1-32: J | Double solenoid | 573717 | VMPA14-M1H-J-PI |
| | 2x 3/2-way valve | | | |
| | Position function 1-32: N | Normally open | 573725 | VMPA14-M1H-N-PI |
| | Position function 1-32: NS | Normally open, mechanical spring return | 575977 | VMPA14-M1H-NS-PI |
| | Position function 1-32: K | Normally closed | 573724 | VMPA14-M1H-K-PI |
| | Position function 1-32: KS | Normally closed, mechanical spring return | 575976 | VMPA14-M1H-KS-PI |
| | Position function 1-32: H | 1x normally open – 1x normally closed | 573726 | VMPA14-M1H-H-PI |
| | Position function 1-32: HS | 1x normally open – 1x normally closed, mechanical spring return | 575979 | VMPA14-M1H-HS-PI |
| | 5/3-way valve | | | |
| | Position function 1-32: B | Mid-position pressurised | 573719 | VMPA14-M1H-B-PI |
| | Position function 1-32: G | Mid-position closed | 573721 | VMPA14-M1H-G-PI |
| | Position function 1-32: E | Mid-position exhausted | 573720 | VMPA14-M1H-E-PI |
| | 3/2-way valve | | | |
| | Position function 1-32: W | Normally open, external compressed air supply | 573723 | VMPA14-M1H-W-PI |
| | Position function 1-32: X | Normally closed, external compressed air supply | 573722 | VMPA14-M1H-X-PI |
| 2x 2/2-way valve | | | | |
| Position function 1-32: D | Normally closed | 573727 | VMPA14-M1H-D-PI | |
| Position function 1-32: DS | Normally closed, mechanical spring return | 575978 | VMPA14-M1H-DS-PI | |
| Position function 1-32: I | 1x Normally closed, 1x Normally closed, reversible | 573728 | VMPA14-M1H-I-PI | |
| Vacant position – Width 14 mm | | | | |
|  | Position function 1-32: L | Blanking plate for one valve position in width 14 mm A self-adhesive label is supplied | 573729 | VMPA14-RP |

Valve terminals MPA-L



Accessories

FESTO

| Ordering data | | | | | | |
|---|---|---|--|---------------|---------------------------------|---------------------------------|
| | Code | Valve function | | | Part No. | Type |
| Sub-base – Width 14 mm | | | | | | |
|  | Duct separation to the right of sub-base 1-40: – | Single, without electrical interlinking module, without cartridge fitting | No duct separation | – | 560973 | VMPAL-AP-14 |
| | Duct separation to the right of sub-base 1-40: T | | Duct 1 separated | – | 560975 | VMPAL-AP-14-T1 |
| | Duct separation to the right of sub-base 1-40: TR | | Ducts 3, 5 separated | – | 560977 | VMPAL-AP-14-T35 |
| | Duct separation to the right of sub-base 1-40: TS | | Ducts 1 and 3, 5 separated | – | 560979 | VMPAL-AP-14-T135 |
|  | – | Single, with electrical interlinking module, single solenoid (for 1 solenoid coil), with cartridge fitting | No duct separation, tubing O.D. | 6 mm | 560995 | VMPAL-AP-14-QS6-1 |
| | | | | 8 mm | 560989 | VMPAL-AP-14-QS8-1 |
| | | | | 1/4" | 561007 | VMPAL-AP-14-QS1/4"-1 |
| | | | | 5/16" | 561001 | VMPAL-AP-14-QS5/16"-1 |
| | | | Duct 1 separated, tubing O.D. | 6 mm | 561019 | VMPAL-AP-14-QS6-1-T1 |
| | | | | 8 mm | 561013 | VMPAL-AP-14-QS8-1-T1 |
| | | | | 1/4" | 561031 | VMPAL-AP-14-QS1/4"-1-T1 |
| | | | | 5/16" | 561025 | VMPAL-AP-14-QS5/16"-1-T1 |
| | | Single, with electrical interlinking module, double solenoid (for 2 solenoid coils), with cartridge fitting | No duct separation, tubing O.D. | 6 mm | 560996 | VMPAL-AP-14-QS6-2 |
| | | | | 8 mm | 560990 | VMPAL-AP-14-QS8-2 |
| | | | | 1/4" | 561008 | VMPAL-AP-14-QS1/4"-2 |
| | | | Duct 1 separated, tubing O.D. | 5/16" | 561002 | VMPAL-AP-14-QS5/16"-2 |
| | | | | 6 mm | 561020 | VMPAL-AP-14-QS6-2-T1 |
| | | | | 8 mm | 561014 | VMPAL-AP-14-QS8-2-T1 |
| | | | 1/4" | 561032 | VMPAL-AP-14-QS1/4"-2-T1 | |
| | | | 5/16" | 561026 | VMPAL-AP-14-QS5/16"-2-T1 | |
| Combination of four sub-bases – Width 14 mm | | | | | | |
|  | Combination manifold block: Z | Without electrical interlinking module, without cartridge fitting | – | – | 560983 | VMPAL-AP-4X14 |
|  | – | With electrical interlinking module, single solenoid (for 1 solenoid coil), with cartridge fitting | No duct separation, tubing O.D. | 6 mm | 561091 | VMPAL-AP-4X14-QS6-1 |
| | | | | 8 mm | 561085 | VMPAL-AP-4X14-QS8-1 |
| | | | | 1/4" | 561103 | VMPAL-AP-4X14-QS1/4"-1 |
| | | | | 5/16" | 561097 | VMPAL-AP-4X14-QS5/16"-1 |
| | | With electrical interlinking module, double solenoid (for 2 solenoid coils), with cartridge fitting | No duct separation, tubing O.D. | 6 mm | 561092 | VMPAL-AP-4X14-QS6-2 |
| | | | | 8 mm | 561086 | VMPAL-AP-4X14-QS8-2 |
| | | | | 1/4" | 561104 | VMPAL-AP-4X14-QS1/4"-2 |
| | | | | 5/16" | 561098 | VMPAL-AP-4X14-QS5/16"-2 |
| Electrical interlinking module – Width 14 mm | | | | | | |
|  | Type of module block 1-40: F | For one sub-base (1 valve position) | Grey – single solenoid (1 solenoid coil) | | 560963 | VMPAL-EVAP-14-1 |
| | Type of module block 1-40: E | | Black – double solenoid (2 solenoid coils) | | 560964 | VMPAL-EVAP-14-2 |
|  | Type of module block 1-40: F | For combination of four sub-bases (4 valve positions) | Grey – single solenoid (4 solenoid coils) | | 560969 | VMPAL-EVAP-14-1-4 |
| | Type of module block 1-40: E | | Black – double solenoid (8 solenoid coils) | | 560970 | VMPAL-EVAP-14-2-4 |












Valve terminals MPA-L

Accessories

| Ordering data | | | | |
|---|--|---|-----------------|-----------------|
| | Code | Valve function | Part No. | Type |
| Individual solenoid valve – Width 20 mm | | | | |
|  | 5/2-way valve | | | |
| | Position function 1-32: M | Single solenoid | 8022034 | VMPA2-M1BH-M-PI |
| | Position function 1-32: MS | Single solenoid, mechanical spring return | 571333 | VMPA2-M1H-MS-PI |
| | Position function 1-32: J | Double solenoid | 8022035 | VMPA2-M1BH-J-PI |
| | 2x 3/2-way valve | | | |
| | Position function 1-32: N | Normally open | 537958 | VMPA2-M1H-N-PI |
| | Position function 1-32: NS | Normally open, mechanical spring return | 568655 | VMPA2-M1H-NS-PI |
| | Position function 1-32: K | Normally closed | 537957 | VMPA2-M1H-K-PI |
| | Position function 1-32: KS | Normally closed, mechanical spring return | 568656 | VMPA2-M1H-KS-PI |
| | Position function 1-32: H | 1x normally open – 1x normally closed | 537959 | VMPA2-M1H-H-PI |
| | Position function 1-32: HS | 1x normally open – 1x normally closed, mechanical spring return | 568658 | VMPA2-M1H-HS-PI |
| | 5/3-way valve | | | |
| | Position function 1-32: B | Mid-position pressurised | 8022036 | VMPA2-M1BH-B-PI |
| | Position function 1-32: G | Mid-position closed | 8022037 | VMPA2-M1BH-G-PI |
| | Position function 1-32: E | Mid-position exhausted | 8022038 | VMPA2-M1BH-E-PI |
| | 1x 3/2-way valve | | | |
| | Position function 1-32: W | Normally open, external compressed air supply | 8022040 | VMPA2-M1BH-W-PI |
| | Position function 1-32: X | Normally closed, external compressed air supply | 8022039 | VMPA2-M1BH-X-PI |
| | 2x 2/2-way valve | | | |
| Position function 1-32: D | Normally closed | 537960 | VMPA2-M1H-D-PI | |
| Position function 1-32: DS | Normally closed, mechanical spring return | 568657 | VMPA2-M1H-DS-PI | |
| Position function 1-32: I | 1x normally closed 1x normally closed, reversible | 543703 | VMPA2-M1H-I-PI | |
| Vacant position – Width 20 mm | | | | |
|  | Position function 1-32: L | Blanking plate for one valve position in width 20 mm A self-adhesive label is supplied | 537962 | VMPA2-RP |




Valve terminals MPA-L

Accessories

| Ordering data | | | | | | | |
|---|-----------------------------|--|------------------------|--------------------------------|--------------------|--|---|
| | Code | Valve function | Part No. | Type | | | |
| Vertical stacking modules – Width 20 mm | | | | | | | |
|  | Pressure regulator 1-32: PA | Pressure regulator plate (with 10 mm cartridge fitting connection for pressure gauge) | For port 1 | 0.5 ... 8.5 bar | 543342 | VMPA2-B8-R1C2-C-10 | |
| | Pressure regulator 1-32: PF | | | 0.5 ... 5 bar | 549055 | VMPA2-B8-R1C2-C-06 | |
| | Pressure regulator 1-32: PC | | For port 2 | 2 ... 8.5 bar | 543343 | VMPA2-B8-R2C2-C-10 | |
| | Pressure regulator 1-32: PH | | | 2 ... 5 bar | 549056 | VMPA2-B8-R2C2-C-06 | |
| | Pressure regulator 1-32: PB | | For port 4 | 2 ... 8.5 bar | 543344 | VMPA2-B8-R3C2-C-10 | |
| | Pressure regulator 1-32: PG | | | 2 ... 5 bar | 549057 | VMPA2-B8-R3C2-C-06 | |
| | Pressure regulator 1-32: PL | | For port 2, reversible | 0.5 ... 8.5 bar | 543347 | VMPA2-B8-R6C2-C-10 | |
| | Pressure regulator 1-32: PN | | | 0.5 ... 5 bar | 549113 | VMPA2-B8-R6C2-C-06 | |
| | Pressure regulator 1-32: PK | | For port 4, reversible | 0.5 ... 8.5 bar | 543348 | VMPA2-B8-R7C2-C-10 | |
| | Pressure regulator 1-32: PM | | | 0.5 ... 5 bar | 549114 | VMPA2-B8-R7C2-C-06 | |
|  | Pressure regulator 1-32: PV | Vertical supply plate | Connecting thread | G1/8 | 8029486 | VMPA2-VSP-0  | |
| | | | | With connector for tubing O.D. | 6 mm | 8035441 | VMPA2-VSP-QS6  |
| | | | | | 8 mm | 8029488 | VMPA2-VSP-QS8  |
| | | | | | 10 mm | 8029489 | VMPA2-VSP-QS10  |
| | | | | | 1/4" | 8035442 | VMPA2-VSP-QS1/4  |
| | | | | | 5/16" | 8029491 | VMPA2-VSP-QS5/16  |
| | | | | | 3/8" | 8029492 | VMPA2-VSP-QS3/8  |
|  | Pressure gauge 1-32: T | Pressure gauge, 10 mm cartridge fitting connection, for pressure regulator plate | Display unit bar/psi | 0 ... 16 bar | 543487 | PAGN-26-16-P10 | |
| | | | | 0 ... 10 bar | 543488 | PAGN-26-10-P10 | |
| | – | | Display unit MPa | 0 ... 1.0 MPa | 563736 | PAGN-26-1M-P10 | |
| | | | | 0 ... 1.6 MPa | 563735 | PAGN-26-1.6M-P10 | |
|  | Pressure gauge 1-32: VF | Threaded adapter from 10 mm cartridge fitting connection to thread G1/8 | | 565811 | QSP-10-G1/8 | | |

Valve terminals MPA-L






Accessories

| Ordering data | | | | | | |
|---|---|---|--|---------------|---------------------------------|---------------------------------|
| | Code | Description | Part No. | Type | | |
| Sub-base – Width 20 mm | | | | | | |
|  | Duct separation to the right of sub-base 1-40: – | Single, without electrical interlinking module, without cartridge fitting | No duct separation | – | 560974 | VMPAL-AP-20 |
| | Duct separation to the right of sub-base 1-40: T | | Duct 1 separated | – | 560976 | VMPAL-AP-20-T1 |
| | Duct separation to the right of sub-base 1-40: TR | | Ducts 3, 5 separated | – | 560978 | VMPAL-AP-20-T35 |
| | Duct separation to the right of sub-base 1-40: TS | | Ducts 1 and 3, 5 separated | – | 560980 | VMPAL-AP-20-T135 |
|  | – | Single, with electrical interlinking module, single solenoid (for 1 solenoid coil), with cartridge fitting | No duct separation, tubing O.D. | 8 mm | 560997 | VMPAL-AP-20-QS8-1 |
| | | | | 10 mm | 560991 | VMPAL-AP-20-QS10-1 |
| | | | | 5/16" | 561009 | VMPAL-AP-20-QS5/16"-1 |
| | | | | 3/8" | 561003 | VMPAL-AP-20-QS3/8"-1 |
| | | | Duct 1 separated, tubing O.D. | 8 mm | 561021 | VMPAL-AP-20-QS8-1-T1 |
| | | | | 10 mm | 561015 | VMPAL-AP-20-QS10-1-T1 |
| | | | | 5/16" | 561033 | VMPAL-AP-20-QS5/16"-1-T1 |
| | | | | 3/8" | 561027 | VMPAL-AP-20-QS3/8"-1-T1 |
| | | Single, with electrical interlinking module, double solenoid (for 2 solenoid coils), with cartridge fitting | No duct separation, tubing O.D. | 8 mm | 560998 | VMPAL-AP-20-QS8-2 |
| | | | | 10 mm | 560992 | VMPAL-AP-20-QS10-2 |
| | | | | 5/16" | 561010 | VMPAL-AP-20-QS5/16"-2 |
| | | | Duct 1 separated, tubing O.D. | 3/8" | 561004 | VMPAL-AP-20-QS3/8"-2 |
| | | | | 8 mm | 561022 | VMPAL-AP-20-QS8-2-T1 |
| | | | | 10 mm | 561016 | VMPAL-AP-20-QS10-2-T1 |
| | | | 5/16" | 561034 | VMPAL-AP-20-QS5/16"-2-T1 | |
| | | | 3/8" | 561028 | VMPAL-AP-20-QS3/8"-2-T1 | |
| Electrical interlinking module – Width 20 mm | | | | | | |
|  | Type of module block 1-40: D | For one sub-base (1 valve position) | Grey – single solenoid (1 solenoid coil) | | 560965 | VMPAL-EVAP-20-1 |
| | Type of module block 1-40: B | | Black – double solenoid (2 solenoid coils) | | 560966 | VMPAL-EVAP-20-2 |

Valve terminals MPA-L

Accessories











FESTO

| Ordering data | | | | | | |
|---|---------------|---|----------|---------------|-----------------------|-----------|
| | Code | Description | Part No. | Type | PU ¹⁾ | |
| Tie rod | | | | | | |
|  | Tie rod: – | Threaded rod for tie rod, width across flats 5 mm The threaded rod/sleeve combination is selected based on the number and width of the individual sub-bases. | 5 mm | 561116 | VMPAL-ZAS-5 | 3 |
| | | | 45 mm | 561117 | VMPAL-ZAS-45 | 3 |
| | | | 85 mm | 561118 | VMPAL-ZAS-85 | 3 |
| | | | 125 mm | 561119 | VMPAL-ZAS-125 | 3 |
| | | | 165 mm | 561120 | VMPAL-ZAS-165 | 3 |
| | | | 205 mm | 561121 | VMPAL-ZAS-205 | 3 |
| | | | 245 mm | 561122 | VMPAL-ZAS-245 | 3 |
| | | | 285 mm | 561123 | VMPAL-ZAS-285 | 3 |
| | | | 325 mm | 561124 | VMPAL-ZAS-325 | 3 |
| | | | 365 mm | 561125 | VMPAL-ZAS-365 | 3 |
| | | | 405 mm | 561126 | VMPAL-ZAS-405 | 3 |
| | | | 445 mm | 561127 | VMPAL-ZAS-445 | 3 |
| | | | 485 mm | 561128 | VMPAL-ZAS-485 | 3 |
| | | | 525 mm | 561129 | VMPAL-ZAS-525 | 3 |
| | | | 565 mm | 561130 | VMPAL-ZAS-565 | 3 |
| | | | 605 mm | 561131 | VMPAL-ZAS-605 | 3 |
| | | | 645 mm | 561132 | VMPAL-ZAS-645 | 3 |
| | | | 685 mm | 561133 | VMPAL-ZAS-685 | 3 |
| 725 mm | 561134 | VMPAL-ZAS-725 | 3 | | | |
| 765 mm | 561175 | VMPAL-ZAS-765 | 3 | | | |
| 805 mm | 561176 | VMPAL-ZAS-805 | 3 | | | |
|  | – | Sleeve, internal hex 4 mm | 36 mm | 561135 | VMPAL-ZAH-36 | 3 |
| | | | 46 mm | 561136 | VMPAL-ZAH-46 | 3 |
| | | | 56 mm | 561137 | VMPAL-ZAH-56 | 3 |
| | | | 66 mm | 561138 | VMPAL-ZAH-66 | 3 |
|  | – | Tie rod extender for subsequently extending the valve terminal by a sub-base in width | 10 mm | 561139 | VMPAL-ZAE-10 | 3 |
| | | | 14 mm | 561140 | VMPAL-ZAE-14 | 3 |
| | | Tie rod extender for subsequently extending the valve terminal by a supply module | 20 mm | 561141 | VMPAL-ZAE-20 | 3 |
| | | | 20 mm | 561141 | VMPAL-ZAE-20 | 3 |
| | | Tie rod extender for subsequently extending the valve terminal by four sub-bases in width | 10 mm | 570779 | VMPAL-ZAE-10-4 | 3 |
| | | | 14 mm | 570780 | VMPAL-ZAE-14-4 | 3 |
|  | – | Screw M4 with internal hex 2.5 mm, for tie rod | 30 mm | 571924 | VMPAL-M4X30 | 3 |
| Screw | | | | | | |
|  | – | Screw M3 and square nut, for linking four sub-bases | 39 mm | 561142 | VMPAL-MS-4x10 | 10 |

1) Packaging unit quantity.

Valve terminals MPA-L

Accessories








| Ordering data | | | | | | |
|---|--|--|-------------|-----------------|--|----|
| | Code | Description | Part No. | Type | PU ¹⁾ | |
| Mounting | | | | | | |
|  | - | Mounting bracket Wall brackets should be mounted max. every 13 cm on the valve terminal | 560949 | VMPAL-BD | 10 | |
| H-rail mounting | | | | | | |
|  | Mounting accessories: H | MPA-L with multi-pin plug connection | 526032 | CPX-CPA-BG-NRH | 3 | |
|  | Mounting accessories: H | MPA-L with fieldbus connection | 560798 | VMPAF-FB-BG-NRH | 2 | |
| Releasing tool | | | | | | |
|  | - | For releasing the electrical interlinking module from the sub-base | 572017 | VMPAL-LW | 1 | |
| Cover cap | | | | | | |
|  | Manual override: N | Cover cap for manual override, non-detenting | 540897 | VMPA-HBT-B | 10 | |
|  | Manual override: V | Cover cap for manual override, covered | 540898 | VMPA-HBV-B | 10 | |
|  | Manual override: Y | Cover cap for manual override, without accessories detenting | 8002234 | VAMC-L1-CD |  10 | |
| Inscription label holder/inscription labels | | | | | | |
|  | Inscription label holder for sub-bases: TM | Holder for inscription label IBS-6x10 | Width 10 mm | 561109 | VMPAL-ST-AP-10 | 10 |
| | | | Width 14 mm | 561112 | VMPAL-ST-AP-14 | 10 |
| | | | Width 20 mm | 561115 | VMPAL-ST-AP-20 | 10 |
|  | - | Inscription label, 6x10 mm | 18576 | IBS-6X10 | 64 | |

1) Packaging unit quantity.

Valve terminals MPA-L






Accessories

FESTO

| Ordering data | | | | |
|---|--|---|---------------|---------------------------------------|
| | Code | Description | Part No. | Type |
| Supply module | | | | |
|  | Type of module block 1-40: U | With electrical interlinking module, without cartridge fitting | 560950 | VMPAL-SP-0 |
|  | Type of module block 1-40: U | With electrical interlinking module, with cartridge fitting for tubing O.D. | 8 mm | 573645 VMPAL-SP-QS8 |
| | | | 10 mm | 560951 VMPAL-SP-QS10 |
| | | | 12 mm | 560952 VMPAL-SP-QS12 |
| | | | 5/16" | 573646 VMPAL-SP-QS5/16" |
| | | | 3/8" | 560953 VMPAL-SP-QS3/8" |
|  | Type of module block 1-40: U | Without electrical interlinking module, without cartridge fitting | 570774 | VMPAL-SP |
| Plate | | | | |
|  | Exhaust port: UD, UE, UF, UM, UN, UP or UG | Exhaust plate for ducted exhaust air | 560956 | VMPAL-EG |
|  | Exhaust port: UE | Exhaust plate for ducted exhaust air, with cartridge fitting for tubing O.D. 10 mm | 560957 | VMPAL-EG-QS10 |
| | Exhaust port: UN | Exhaust plate for ducted exhaust air, with cartridge fitting for tubing O.D. 3/8" | 560959 | VMPAL-EG-QS3/8" |
|  | Exhaust port: – | Flat plate silencer | 560955 | VMPAL-EU |
| Electrical interlinking module | | | | |
|  | Type of module block 1-40: U | Black for supply module (signals are passed through) | 571011 | VMPAL-EVAP-20-SP |

Valve terminals MPA-L

Accessories






| Ordering data | | | | | |
|---|----------------------------|---|---|---------------------|----------------------------|
| | Code | Description | Part No. | Type | |
| Right-hand end plate | | | | | |
|  | Right-hand end plate: - | Low, with ports 12/14, 82/84, with pilot air selector for choosing the pilot air supply (internal or external) | 560945 | VMPAL-EPR | |
|  | Right-hand end plate: D | High, with ports 1, 3, 5, 12/14, 82/84, with pilot air selector for choosing the pilot air supply (internal or external), reverse operation possible | 560947 | VMPAL-EPR-SP | |
| Left-hand end plate | | | | | |
|  | Electrical connection: MS2 | Electrical interface for multi-pin plug connection, IP40 | Sub-D, 9-pin, 8 addresses | 570777 | VMPAL-EPL-SD9-IP40 |
| | Electrical connection: MS1 | | Sub-D, 25-pin, 24 addresses | 560940 | VMPAL-EPL-SD25-IP40 |
| | Electrical connection: MS3 | | Sub-D, 44-pin, 32 addresses | 560941 | VMPAL-EPL-SD44-IP40 |
| | Electrical connection: MF1 | | Flat cable, 40-pin, 32 addresses | 560942 | VMPAL-EPL-FL40-IP40 |
| | Electrical connection: MC | | Terminal strip, 33-pin, 32 addresses | 560943 | VMPAL-EPL-KL33-IP40 |
| | Electrical connection: MS6 | Electrical interface for multi-pin plug connection | Sub-D, 25-pin, 24 addresses | 560938 | VMPAL-EPL-SD25 |
| | Electrical connection: MS8 | | Sub-D, 44-pin, 32 addresses | 560939 | VMPAL-EPL-SD44 |
|  | Electrical connection: CX | Pneumatic interface for CPX terminal | 32 addresses | 570783 | VMPAL-EPL-CPX |
|  | Electrical connection: LK | Node with IO-Link | 32 addresses | 575667 | VMPAL-EPL-IPO32 |
| | Electrical connection: PT | Node with I-Port interface | | | |

1) A self-adhesive label is supplied.

Valve terminals MPA-L

Accessories










FESTO

| Ordering data | | | | | | |
|---|---|---|--|--------------|----------------------------|----------------------------|
| | Code | Description | Part No. | Type | | |
| Connecting cable for multi-pin plug connection with Sub-D plug socket | | | | | | |
|  | Connecting cable: DA | Socket 9-pin, Sub-D, open cable end 9-pin | 2.5 m | 531184 | KMP6-09P-08-2,5 | |
| | Connecting cable: DB | | | 5 m | 531185 | KMP6-09P-08-5 |
| | Connecting cable: DC | | | 10 m | 531186 | KMP6-09P-08-10 |
| | – | Socket 25-pin, Sub-D, open cable end 15-pin | 2.5 m | 530049 | KMP6-25P-12-2,5 | |
| | – | | | 5 m | 530050 | KMP6-25P-12-5 |
| | – | | | 10 m | 530051 | KMP6-25P-12-10 |
| | Connecting cable: DD | Socket 25-pin, Sub-D, open cable end 25-pin | 2.5 m | 530046 | KMP6-25P-20-2,5 | |
| | Connecting cable: DK | | | 5 m | 530047 | KMP6-25P-20-5 |
| | Connecting cable: DF | | | 10 m | 530048 | KMP6-25P-20-10 |
| | Connecting cable: DG | Socket 44-pin, Sub-D, open cable end 44-pin | 2.5 m | 575113 | NEBV-S1G44-K-2.5-N-LE44-S6 | |
| | Connecting cable: DH | | | 5 m | 575114 | NEBV-S1G44-K-5-N-LE44-S6 |
| | Connecting cable: DJ | | | 10 m | 575115 | NEBV-S1G44-K-10-N-LE44-S6 |
| |  | Connecting cable: CA | Cable outlet to front (only with left-hand end plate MS6) | 25-pin | 2.5 m | 560416 |
| Connecting cable: CB | | 5 m | | | 560417 | VMPAL-KM-V-SD25-IP67-5 |
| Connecting cable: CC | | 10 m | | | 560418 | VMPAL-KM-V-SD25-IP67-10 |
| – | | 0.5 ... 30 m | | | 562389 | VMPAL-KM-V-SD25-IP67-X |
| Connecting cable: CQ | | Cable outlet to front (only with left-hand end plate MS6), suitable for use with energy chains | 25-pin | 2.5 m | 560410 | VMPAL-KMSK-V-SD25-IP67-2,5 |
| Connecting cable: CR | | | | 5 m | 560411 | VMPAL-KMSK-V-SD25-IP67-5 |
| Connecting cable: CS | | | | 10 m | 560412 | VMPAL-KMSK-V-SD25-IP67-10 |
| – | | | | 0.5 ... 30 m | 562391 | VMPAL-KMSK-V-SD25-IP67-X |
| Connecting cable: CJ | | Cable outlet to front (only with left-hand end plate MS8) | 44-pin | 2.5 m | 560422 | VMPAL-KM-V-SD44-IP67-2,5 |
| Connecting cable: CK | | | | 5 m | 560423 | VMPAL-KM-V-SD44-IP67-5 |
| Connecting cable: CL | | | | 10 m | 560424 | VMPAL-KM-V-SD44-IP67-10 |
| – | | | | 0.5 ... 30 m | 562390 | VMPAL-KM-V-SD44-IP67-X |
|  | | Connecting cable: CD | Cable outlet to side (only with left-hand end plate MS6) | 25-pin | 2.5 m | 560419 |
| | Connecting cable: CE | 5 m | | | 560420 | VMPAL-KM-S-SD25-IP67-5 |
| | Connecting cable: CH | 10 m | | | 560421 | VMPAL-KM-S-SD25-IP67-10 |
| | – | 0.5 ... 30 m | | | 562392 | VMPAL-KM-S-SD25-IP67-X |
| | Connecting cable: CT | Cable outlet to side (only with left-hand end plate MS6), suitable for use with energy chains | 25-pin | 2.5 m | 560413 | VMPAL-KMSK-S-SD25-IP67-2,5 |
| | Connecting cable: CU | | | 5 m | 560414 | VMPAL-KMSK-S-SD25-IP67-5 |
| | Connecting cable: CV | | | 10 m | 560415 | VMPAL-KMSK-S-SD25-IP67-10 |
| | – | | | 0.5 ... 30 m | 562394 | VMPAL-KMSK-S-SD25-IP67-X |
| | Connecting cable: CM | Cable outlet to side (only with left-hand end plate MS8) | 44-pin | 2.5 m | 560425 | VMPAL-KM-S-SD44-IP67-2,5 |
| | Connecting cable: CN | | | 5 m | 560426 | VMPAL-KM-S-SD44-IP67-5 |
| | Connecting cable: CP | | | 10 m | 560427 | VMPAL-KM-S-SD44-IP67-10 |
| | – | | | 0.5 ... 30 m | 562393 | VMPAL-KM-S-SD44-IP67-X |
| | Cover for multi-pin plug connection without connecting cable with Sub-D plug socket | | | | | |
|  | Electrical multi-pin plug cover: EZ | Cable outlet to side or front (only with left-hand end plate MS6) | 25-pin | – | 560428 | VMPAL-KM-SD25-IP67-0 |
| | Electrical multi-pin plug cover: EY | Outlet either to the side or front (only with left-hand end plate MS8) | 44-pin | – | 560429 | VMPAL-KM-SD44-IP67-0 |
| Plug connector | | | | | | |
|  | – | Pre-assembled plug connector for flat cable, 40-pin, for flat cable cross section 0.08 ... 0.13 mm ² | | 570895 | NECU-FCG40-K | |

Valve terminals MPA-L

Accessories

FESTO






| Ordering data | | | | | | | |
|---|---|---|--|---|------------------|----------------|---------|
| | Code | Description | Part No. | Type | PU ¹⁾ | | |
| Cartridge fitting for sub-base in width 10 mm | | | | | | | |
|  | Standard connection for valve size 10 mm: | AA | 10 mm cartridge fitting, plastic, for working lines, connection for tubing O.D. | 3 mm | 132621 | QSPKG10-3 | 10 |
| | | AB | | 4 mm | 132622 | QSPKG10-4 | 10 |
| | | - | | 6 mm | 132623 | QSPKG10-6 | 10 |
| | | AJ | | 1/8" | 132852 | QSPKG10-1/8-U | 10 |
| | | AQ | | 5/32" | 132624 | QSPKG10-5/32-U | 10 |
| | | AK | | 3/16" | 132625 | QSPKG10-3/16-U | 10 |
| | | AL | | 1/4" | 132626 | QSPKG10-1/4-U | 10 |
| | | - | | 10 mm cartridge fitting, nickel-plated brass, for working lines, connection for tubing O.D. | 4 mm | 172972 | QSP10-4 |
| | - | 6 mm | 172973 | QSP10-6 | 10 | | |
| |  | - | 10 mm cartridge fitting, plastic, L-shape, for working lines, connection for tubing O.D. | 3 mm | 132853 | QSPLKG10-3 | 10 |
| - | | 4 mm | | 132920 | QSPLKG10-4 | 10 | |
| - | | 6 mm | | 132921 | QSPLKG10-6 | 10 | |
| - | | 1/8" | | 132854 | QSPLKG10-1/8-U | 10 | |
| - | | 5/32" | | 132922 | QSPLKG10-5/32-U | 10 | |
| - | | 3/16" | | 132923 | QSPLKG10-3/16-U | 10 | |
| - | | 1/4" | | 132924 | QSPLKG10-1/4-U | 10 | |
|  | - | 10 mm cartridge fitting, plastic, long L-shape, for working lines, connection for tubing O.D. | 3 mm | 132861 | QSPLLKG10-3 | 10 | |
| | - | | 4 mm | 132925 | QSPLLKG10-4 | 10 | |
| | - | | 6 mm | 132926 | QSPLLKG10-6 | 10 | |
| | - | | 1/8" | 132862 | QSPLLKG10-1/8-U | 10 | |
| | - | | 5/32" | 132927 | QSPLLKG10-5/32-U | 10 | |
| | - | | 3/16" | 132928 | QSPLLKG10-3/16-U | 10 | |
| | - | | 1/4" | 132929 | QSPLLKG10-1/4-U | 10 | |
| Cartridge fitting for sub-base in width 14 mm | | | | | | | |
|  | Standard connection for valve size 14 mm: | BC | 14 mm cartridge fitting, plastic, for working lines, connection for tubing O.D. | 6 mm | 132930 | QSPKG14-6 | 10 |
| | | - | | 8 mm | 132931 | QSPKG14-8 | 10 |
| | | BL | | 1/4" | 132932 | QSPKG14-1/4-U | 10 |
| | | BQ | | 5/16" | 132933 | QSPKG14-5/16-U | 10 |
|  | - | 14 mm cartridge fitting, plastic, L-shape, for working lines, connection for tubing O.D. | 6 mm | 132938 | QSPLKG14-6 | 10 | |
| | - | | 8 mm | 132939 | QSPLKG14-8 | 10 | |
| | - | | 1/4" | 132940 | QSPLKG14-1/4-U | 10 | |
| | - | | 5/16" | 132941 | QSPLKG14-5/16-U | 10 | |
|  | - | 14 mm cartridge fitting, plastic, long L-shape, for working lines, connection for tubing O.D. | 6 mm | 132942 | QSPLLKG14-6 | 10 | |
| | - | | 8 mm | 132943 | QSPLLKG14-8 | 10 | |
| | - | | 1/4" | 132944 | QSPLLKG14-1/4-U | 10 | |
| | - | | 5/16" | 132945 | QSPLLKG14-5/16-U | 10 | |
| Cartridge fitting for sub-base in width 20 mm | | | | | | | |
|  | Standard connection for valve size 20 mm: | CD | 18 mm cartridge fitting, plastic, for working lines, connection for tubing O.D. | 8 mm | 132649 | QSPKG18-8 | 10 |
| | | - | | 10 mm | 132650 | QSPKG18-10 | 10 |
| | | CQ | | 5/16" | 132651 | QSPKG18-5/16-U | 10 |
| | | CT | | 3/8" | 132652 | QSPKG18-3/8-U | 10 |
|  | - | 18 mm cartridge fitting, plastic, L-shape, for working lines, connection for tubing O.D. | 8 mm | 132946 | QSPLKG18-8 | 10 | |
| | - | | 10 mm | 132947 | QSPLKG18-10 | 10 | |
| | - | | 5/16" | 132948 | QSPLKG18-5/16-U | 10 | |
| | - | | 3/8" | 132949 | QSPLKG18-3/8-U | 10 | |
|  | - | 18 mm cartridge fitting, plastic, long L-shape, for working lines, connection for tubing O.D. | 8 mm | 132950 | QSPLLKG18-8 | 10 | |
| | - | | 10 mm | 132951 | QSPLLKG18-10 | 10 | |
| | - | | 5/16" | 132952 | QSPLLKG18-5/16-U | 10 | |
| | - | | 3/8" | 132953 | QSPLLKG18-3/8-U | 10 | |

1) Packaging unit.

Valve terminals MPA-L

Accessories

FESTO










| Ordering data | | | | | | |
|---|---|--|----------|----------------|------------------|----|
| | Code | Description | Part No. | Type | PU ¹⁾ | |
| Cartridge fitting for supply module | | | | | | |
|  | - | 20 mm cartridge fitting, plastic, for supply ports, connection for tubing O.D. | 8 mm | 132633 | QSPKG20-8 | 10 |
| | | | 10 mm | 132634 | QSPKG20-10 | 10 |
| | | | 12 mm | 132635 | QSPKG20-12 | 10 |
| | | | 5/16" | 132636 | QSPKG20-5/16-U | 10 |
| | | | 3/8" | 132637 | QSPKG20-3/8-U | 10 |
| | | | 1/2" | 132638 | QSPKG20-1/2-U | 10 |
|  | - | 20 mm cartridge fitting, plastic, L-shape, for supply ports, connection for tubing O.D. | 8 mm | 132855 | QSPLKG20-8 | 10 |
| | | | 10 mm | 132856 | QSPLKG20-10 | 10 |
| | | | 12 mm | 132857 | QSPLKG20-12 | 10 |
| | | | 5/16" | 132858 | QSPLKG20-5/16-U | 10 |
| | | | 3/8" | 132859 | QSPLKG20-3/8-U | 10 |
| | | | 1/2" | 132860 | QSPLKG20-1/2-U | 10 |
|  | - | 20 mm cartridge fitting, plastic, long L-shape, for supply ports, connection for tubing O.D. | 8 mm | 132863 | QSPLLKG20-8 | 10 |
| | | | 10 mm | 132864 | QSPLLKG20-10 | 10 |
| | | | 12 mm | 132865 | QSPLLKG20-12 | 10 |
| | | | 5/16" | 132866 | QSPLLKG20-5/16-U | 10 |
| | | | 3/8" | 132867 | QSPLLKG20-3/8-U | 10 |
| | | | 1/2" | 132868 | QSPLLKG20-1/2-U | 10 |
| Adapter for sub-bases | | | | | | |
|  | Standard connection for valve size 10 mm: AGG | Adapter from 10 mm cartridge fitting connection to thread M7 | 572380 | VMPAL-F10-M7 | 10 | |
| | Standard connection for valve size 14 mm: BGG | Adapter from 14 mm cartridge fitting connection to thread G1/8 | 574084 | VMPAL-F14-G1/8 | 10 | |
| | Standard connection for valve size 20 mm: CGG | Adapter from 18 mm cartridge fitting connection to thread G1/4 | 573914 | VMPAL-F20-G1/4 | 10 | |
| Adapter for supply module/plate | | | | | | |
|  | - | Adapter from 20 mm cartridge fitting connection to thread G1/4 | 572381 | VMPAL-FSP-G1/4 | 10 | |

1) Packaging unit.

Valve terminals MPA-L

Accessories

FESTO






| Ordering data | | | | | | |
|---|---------------|---|----------------------|----------------------|-----------------------|------------|
| | Code | Description | Part No. | Type | PU ¹⁾ | |
| Push-in fitting | | | | | | |
|  | - | Connecting thread M7 with sealing ring, with internal hex, for tubing O.D. | 4 mm | 153319 | QSM-M7-4-I | 10 |
| | | | 6 mm | 153321 | QSM-M7-6-I | 10 |
|  | - | Connecting thread G1/4 with sealing ring, with internal hex, for tubing O.D. | 6 mm | 186108 | QS-G1/4-6-I | 10 |
| | | | | | | |
|  | - | Connecting thread G1/4 with sealing ring, with external hex, for tubing O.D. | 6 mm | 186097 | QS-G1/4-6 | 10 |
| | | | 8 mm | 186099 | QS-G1/4-8 | 10 |
| | | | 10 mm | 186101 | QS-G1/4-10 | 10 |
| | | Connecting thread G1/4, metal, with external hex, for tubing O.D. | 6 mm | 193411 | QS-F-G1/4-6 | 10 |
| | | | 8 mm | 193412 | QS-F-G1/4-8 | 10 |
| | | | 10 mm | 193413 | QS-F-G1/4-10 | 10 |
| | | | 12 mm | 533848 | QS-F-G1/4-12 | 10 |
| | | | | | | |
|  | - | Connecting thread G1/4, metal, with internal hex, for tubing O.D. | 8 mm | 533930 | QS-F-G1/4-8-I | 10 |
| | | | 10 mm | 533931 | QS-F-G1/4-10-I | 10 |
|  | - | Connecting thread G1/4, metal, with push-in sleeve \varnothing | 6 mm | 533881 | QS-F-G1/4-6H | 10 |
| | | | 8 mm | 533882 | QS-F-G1/4-8H | 10 |
| | | | 10 mm | 533883 | QS-F-G1/4-10H | 10 |
| | | | 12 mm | 533884 | QS-F-G1/4-12H | 10 |
|  | - | Connecting thread G1/4, with external hex, flame-retardant, for tubing O.D. | 6 mm | 186316 | QS-VO-G1/4-6 | 10 |
| | | | 8 mm | 186317 | QS-VO-G1/4-8 | 10 |
| | | | 10 mm | 186318 | QS-VO-G1/4-10 | 10 |
| Push-in L-connector | | | | | | |
|  | - | Push-in sleeve \varnothing | 6 mm | 153057 | QSL-6H | 10 |
| | | | 8 mm | 153058 | QSL-8H | 10 |
| | | Long push-in sleeve \varnothing | 6 mm | 153066 | QSL-6HL | 10 |
|  | - | Push-in fitting with sealing ring, connecting thread M7, with external hex, for tubing O.D. | 4 mm | 186352 | QSML-M7-4 | 10 |
| | | | | 130773 | QSML-M7-4-100 | 100 |
| | | | 6 mm | 186353 | QSML-M7-6 | 10 |
| | | 130774 | QSML-M7-6-100 | 100 | | |
| | - | Long push-in fitting with sealing ring, connecting thread M7, with external hex, for tubing O.D. | 4 mm | 186354 | QSMML-M7-4 | 10 |
| | | | 6 mm | 186355 | QSMML-M7-6 | 10 |
| | - | Push-in fitting with sealing ring, connecting thread G1/4, with external hex, for tubing O.D. | 6 mm | 186118 | QSL-G1/4-6 | 10 |
| | | | 8 mm | 186120 | QSL-G1/4-8 | 10 |
| | | | 10 mm | 186122 | QSL-G1/4-10 | 10 |
| | | Push-in fitting, metal, with sealing ring, connecting thread G1/4, with external hex, for tubing O.D. | 6 mm | 193421 | QSL-F-G1/4-6 | 10 |
| | | | 8 mm | 193422 | QSL-F-G1/4-8 | 10 |
| | | | 10 mm | 193423 | QSL-F-G1/4-10 | 10 |
| Long push-in fitting, metal, connecting thread G1/4, with external hex, for tubing O.D. | | 6 mm | 533853 | QSL-F-G1/4-12 | 10 | |
| | | 12 mm | 533853 | QSL-F-G1/4-12 | 10 | |
| | | 6 mm | 556846 | QSL-F-G1/4-6 | 10 | |
| 8 mm | 556847 | QSL-F-G1/4-8 | 10 | | | |
| | 10 mm | 556848 | QSL-F-G1/4-10 | 10 | | |
| | 12 mm | 556849 | QSL-F-G1/4-12 | 10 | | |
|  | - | Push-in fitting, connecting thread G1/4, with internal hex, for tubing O.D. | 6 mm | 186149 | QSLV-G1/4-6-I | 10 |
| | | | 8 mm | 186151 | QSLV-G1/4-8-I | 10 |

1) Packaging unit.

Valve terminals MPA-L

Accessories

FESTO

| Ordering data | | | | | | |
|---|-------------------|--|----------|---------------|---------------------|-----------|
| | Code | Description | Part No. | Type | PU ¹⁾ | |
| Push-in fitting, self-sealing | | | | | | |
|  | - | With sealing ring, with external hex, connecting thread G1/4, for tubing O.D. | 6 mm | 186296 | QSK-G1/4-6 | 1 |
| | | | 8 mm | 186298 | QSK-G1/4-8 | 1 |
| | | | 10 mm | 186300 | QSK-G1/4-10 | 1 |
| | | With sealing ring, with external hex, L shape, connecting thread G1/4, for tubing O.D. | 6 mm | 186306 | QSKL-G1/4-6 | 1 |
| | | | 8 mm | 186308 | QSKL-G1/4-8 | 1 |
| | | | 10 mm | 186310 | QSKL-G1/4-10 | 1 |
| Rotary push-in fitting | | | | | | |
|  | - | With external hex, connecting thread G1/4, for tubing O.D. | 6 mm | 186278 | QSR-G1/4-6 | 1 |
| | | | 8 mm | 186280 | QSR-G1/4-8 | 1 |
| | | With external hex, L-shape, connecting thread G1/4, for tubing O.D. | 6 mm | 186287 | QSRL-G1/4-6 | 1 |
| | | | 8 mm | 186289 | QSRL-G1/4-8 | 1 |
| Silencer | | | | | | |
|  | - | Connecting thread | M7 | 161418 | UC-M7 | 1 |
| | | | | 534218 | UC-M7-50 | 50 |
| | | | G1/4 | 165004 | UC-1/4 | 1 |
| | | | | 534220 | UC-1/4-20 | 20 |
| Blanking plug | | | | | | |
|  | - | Thread | M7 | 174309 | B-M7 | 10 |
| | | | G3/8 | 3570 | B-3/8 | 10 |
| | | Cartridge fitting | 10 mm | 172976 | QSP10-PTB | 1 |
| | | | 14 mm | 172987 | QSP14-PTB | 1 |
| | | | 18 mm | 172996 | QSP17-PTB | 1 |
| Manual | | | | | | |
|  | Documentation: DE | MPA-L Pneumatic Components | German | 556353 | P.BE-MPAL-DE | |
| | Documentation: EN | | English | 556354 | P.BE-MPAL-EN | |
| | Documentation: FR | | French | 556356 | P.BE-MPAL-FR | |
| | Documentation: ES | | Spanish | 556355 | P.BE-MPAL-ES | |
| | Documentation: IT | | Italian | 556357 | P.BE-MPAL-IT | |
| | Documentation: SV | | Swedish | 556358 | P.BE-MPAL-SV | |

1) Packaging unit.