



Solenoid valves VUVG/valve terminals VTUG



Solenoid valves VUVG

Key features

FESTO



Innovative

- Both internal and external pilot air supply can be used for manifolds with sub-base valves
- Connection technology easy to change via the E-box
- Max. pressure 10 bar

Versatile

- Wide range of valve functions
- Choice of quick plug connectors
- In-line valves can be used as individual valves or manifold valves
- M5 and M7 in-line valves can be combined on one manifold rail
- Identical sub-base valves for M5 or M7 manifold rail
- Manifolds with pressure zones
- IP40, IP65

Reliable

- Sturdy and durable metal components
 - Valves
 - Manifold rails
- Fast troubleshooting thanks to 360° LED display
- Convenient servicing thanks to valves that can be replaced quickly and easily
- Choice of manual override: non-detenting, detenting or covered

Easy to mount

- Secure mounting on wall or H-rail
- Easy mounting thanks to captive screws and seal
- Connection technology easy to change via the E-box
- Inscription label holder for labelling

Valve terminal configurator

A valve terminal configurator is available to help you select a suitable valve terminal VTUG. This makes it much easier to order the right product. Valve terminals VTUG are ordered via an identcode.

All valve terminals are supplied fully assembled and individually tested. This reduces assembly and installation time to a minimum.

Download CAD data → www.festo.com


Ordering system for valve terminal VTUG

- Individual electrical connection
- Internet: vtug


Solenoid valves VUVG

Key features – Pneumatic components


Individual valves and valve manifolds




In-line valve VUVG-L as individual valve




In-line valve VUVG-S for manifold assembly



Valve manifold VTUG consisting of in-line valves VUVG-S




Sub-base valve VUVG-B for manifold assembly




Valve manifold VTUG consisting of sub-base valves VUVG-B

Basic valves VUVG




- Width 10 mm and 14 mm
- In-line valves
- Sub-base valves
- 2x3/2-way, 5/2-way and 5/3-way valves

E-boxes



- 5, 12 and 24 V DC
- With or without holding current reduction
- LED

Basic valve and E-box combinations




- Note
More E-boxes → page 61

Solenoid valves VUVG

Key features – Pneumatic components


FESTO

Cover caps for manual override



- Closed cover cap for covering the manual override
- Slotted cover cap for enabling only non-detenting operation of the manual override

Inscription label holder



- The inscription label holder can be used in place of the slotted cover cap
- The hinged inscription label holder covers the mounting screw and the manual override

Valve terminal configurator

Download CAD data → www.festo.com


A valve terminal configurator is available to help you select a suitable valve terminal VTUG. This makes it much easier to order the right product. Valve terminals VTUG are ordered via an identcode.

All valve terminals are supplied fully assembled and individually tested. This reduces assembly and installation time to a minimum.

Ordering system for valve terminal VTUG


- Individual electrical connection
- Internet: vtug

Manifold rail for in-line valves



- For in-line valves M3, M5, M7 and G $\frac{1}{8}$, width 10
- For 2x3/2-way, 5/2-way and 5/3-way valves
- 2 to 10 and 12, 14, 16 valve positions

Manifold rail for sub-base valves



- For sub-base valves 10, 10A and 14, width 10
- Manifold rail with M5 or M7 working ports
- For 2x3/2-way, 5/2-way and 5/3-way valves
- 2 to 10, 12, 14 and 16 valve positions
- The sub-base valves always have external pilot air. The pilot air is set via the manifold rail. A short and a long blanking plug are included with the manifold rail for this purpose.

-  - Note

Pressurisation and exhaust at both ends is recommended for an optimised flow rate in cases where there are multiple valves switching simultaneously.

Blanking plate for vacant position



- Vacant position cover

Supply plate



- For additional air supply and exhaust via a valve position

Separator for pressure zones




- For creating multiple pressure zones in a valve manifold

Solenoid valves VUVG

Key features – Pneumatic components

Vertical pressure supply plate

For semi in-line valves M5/M7 and G1/8



- 1 Semi in-line valve VUVG
- 2 Vertical pressure supply plate
- 3 Manifold rail

The vertical pressure supply plate enables separate pressure supply and exhausting for the valve mounted on it. If two vertical pressure supply plates are mounted one on top of the other, the valve mounted on top can be supplied with compressed air and exhausted completely independently of the valve terminal (terminal code CS).

| Code | Diagram | Type | Width | | Description |
|------|---------|-------------|-------|------|-------------------------------------------------------------------------------------------------------------------------------------------|
| | | | M5/M7 | G1/8 | |
| ZU | | VABF-L1-P3A | ■ | ■ | Plate with port 1 for supplying an individual operating pressure or separate exhausting (reverse operation) for a valve position. |
| ZV | | VABF-L1-P7A | ■ | ■ | Plate with ports 3 and 5 for exhausting the valve or supplying an individual operating pressure (reverse operation) for a valve position. |

Solenoid valves VUVG

Key features – Pneumatic components

Creating pressure zones and separating exhaust air

Compressed air is supplied and exhausted via the manifold rail and via supply plates.

The position of the supply plates and duct separations can be freely selected with the VUVG.






Pressure zones are created by isolating the internal supply ducts between the manifold sub-bases by means of appropriate duct separation.

Pressure zone separation can be used for the following ducts:


- Duct 1
- Duct 3
- Duct 5

 Note

- Use a separator if the exhaust air pressures are high
- Use at least one supply plate/supply for each pressure zone
- Pressure zone separation is not possible with pilot air supply (duct 12/14)

| Duct separation | Description |
|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | <p>The pressure zones can be freely configured with the VUVG. The following duct separations are possible:</p> <ul style="list-style-type: none"> • Duct 1 closed  • Duct 1/3/5 closed  • Duct 3/5 closed  |
|  | <p>The number of pressure zones with the VUVG is only limited by the number of valve positions on the manifold rail. Note that each supply plate occupies one valve position.</p> |

Separator VABD



 Note

As the separators are mounted from only one side using a slotted screwdriver, several pressure zones can be created in one profile.

Solenoid valves VUVG

Key features – Pneumatic components

Pilot air supply

Internal pilot air supply

Internal pilot air supply can be chosen with an operating pressure in the range 1.5 ... 8 bar, 2.5 ... 8 bar or 3 ... 8 bar (depending on the valve used).

The pilot air supply is branched from duct 1 (compressed air supply) using an internal connection.


External pilot air supply

External pilot air supply is required for vacuum operation. The port for external pilot air supply (port 12/14) is located on the valve in the case of in-line valves and on the manifold rail in the case of sub-base valves.

Pilot exhaust air port

With sub-base valves, the pilot air is exhausted via duct 82/84 of the manifold rail. With in-line valves, the pilot exhaust air escapes via exhaust holes.

Pilot air supply with in-line and semi in-line valves



- 1 QS fitting for external pilot air at port 12/14
- 2 Single solenoid valve with external pilot air supply
- 3 Single solenoid valve with internal pilot air supply
- 4 Double solenoid valve with external pilot air supply
- 5 Double solenoid valve with internal pilot air supply


The internal pilot air is branched from port 1 in the valve body. The external pilot air (port 12/14) is supplied individually at each valve housing.



Note

Semi in-line valves cannot be supplied centrally with external pilot air via the manifold rail.

Pilot air supply with sub-base valves



- 1 Blanking plug, short, with internal pilot air
- 2 Blanking plug for duct 12/14 with internal pilot air
- 3 Blanking plug, long, with external pilot air
- 4 QS fitting for duct 12/14 with external pilot air

The manifold rails for sub-base valves have an internal conduit between duct 12/14 and duct 1. Internal or external pilot air supply is selected by inserting a blanking plug into this conduit.

Solenoid valves VUVG

Key features – Pneumatic components

Operation with different pressures

Vacuum operation Reverse operation

Points to note with 3/2-way valves

The 3/2-way valves are available in a design with two valves in one valve body and with pneumatic spring return. With these valves, the energy for the return movement is obtained from port 1.


Vacuum operation is therefore only possible at port 3 and 5, not at port 1.

With external pilot air supply, vacuum can be connected at port 1, 3, 5 with the 5/2-way and 5/3-way valves.

The 3/2-way valves with pneumatic spring are not suitable for reverse operation, since at least the minimum pilot pressure must be present in duct 1.

 Note
Pressure must be present at port 1.

Pressure deflector (internal pilot air)



- If two different pressures are required.
- Different pressures can be supplied at duct 1, 3 and 5.


 Note

- With internal pilot air, the minimum pilot pressure must be adhered to in duct 1
- With 2x3/2-way valves without spring return, the minimum pilot pressure must always be adhered to in duct 1

Advantages

- Any pressure or vacuum can be connected at duct 3 and 5 both with external and internal pilot air

Vacuum, ejector pulse and normal position






Vacuum, ejector pulse and normal position with internal pilot air can be achieved by connecting vacuum



at duct 3 and pressure for the ejector pulse at duct 1.

Solenoid valves VUVG

Product range overview

| Design | Working port | Type code | Functions and flow rate [l/min] | | | | | | | | | | | | → Page/ Internet |
|-----------------------------------------------------------------------------------|--------------|-----------|---------------------------------|-------|-------|--------|--------|--------|-------|-------|-------|-------|-------|-------|---------------------|
| | | | T32C | T32U | T32H | T32C/M | T32U/M | T32H/M | M52 | M52/M | B52 | P53C | P53U | P53E | |
| In-line valve as individual valve, solenoid valve VUVG-L | | | | | | | | | | | | | | | |
|  | M3 | 10A | - | - | - | - | - | - | 100 | 80 | 100 | 90 | 90 | 90 | 16 |
| | M5 | 10 | 150 | 150 | 150 | 135 | 125 | 125 | 220 | 190 | 220 | 210 | 210 | 210 | 22 |
| | M7 | 10 | 190 | 190 | 190 | 150 | 140 | 140 | 380 | 320 | 380 | 320 | 320 | 320 | 24 |
| | G1/8 | 14 | 650 | 600 | 650 | 550 | 500 | 500 | 780 | 780 | 780 | 650 | 600 | 600 | 29 |
| | G1/4 | 18 | 1,000 | 1,000 | 1,000 | 1,000 | 1,000 | 1,000 | 1,300 | 1,300 | 1,380 | 1,200 | 1,000 | 1,000 | 34 |
| In-line valve for manifold assembly, solenoid valve VUVG-S | | | | | | | | | | | | | | | |
|  | M3 | 10A | - | - | - | - | - | - | 100 | 80 | 100 | 90 | 90 | 90 | 16 |
| | M5 | 10 | 150 | 150 | 150 | 135 | 125 | 125 | 220 | 190 | 220 | 210 | 210 | 210 | 22 |
| | M7 | 10 | 170 | 170 | 170 | 140 | 130 | 130 | 340 | 290 | 340 | 300 | 300 | 300 | 24 |
| | G1/8 | 14 | 620 | 580 | 580 | 520 | 480 | 480 | 730 | 730 | 730 | 620 | 580 | 580 | 29 |
| | G1/4 | 18 | 1,000 | 1,000 | 1,000 | 1,000 | 1,000 | 1,000 | 1,300 | 1,300 | 1,380 | 1,200 | 1,000 | 1,000 | 34 |

| Design | Working port | Type code | Functions and flow rate [l/min] | | | | | | | | | | | | → Page/ Internet |
|-------------------------------------------------------------------------------------|--------------|-----------|---------------------------------|------|------|--------|--------|--------|-------|-------|-------|------|------|------|---------------------|
| | | | T32C | T32U | T32H | T32C/M | T32U/M | T32H/M | M52 | M52/M | B52 | P53C | P53U | P53E | |
| Sub-base valve, solenoid valve VUVG-B | | | | | | | | | | | | | | | |
|  | M5 | 10A | - | - | - | - | - | - | 100 | 80 | 100 | 90 | 90 | 90 | 39 |
| | M5 | 10 | 150 | 150 | 150 | 130 | 120 | 120 | 210 | 180 | 210 | 200 | 200 | 200 | 44 |
| | M7 | 10 | 160 | 160 | 160 | 140 | 130 | 130 | 270 | 230 | 270 | 250 | 250 | 250 | 44 |
| | G1/8 | 14 | 540 | 510 | 540 | 430 | 410 | 410 | 580 | 580 | 580 | 540 | 510 | 510 | 49 |
| | G1/4 | 18 | 800 | 800 | 800 | 800 | 800 | 800 | 1,000 | 1,000 | 1,000 | 950 | 950 | 950 | 54 |

| Design | Working port | Type code | Description | → Page/ Internet |
|-------------------------------------------------------------------------------------|--------------|-----------|-----------------------------------|---------------------|
| Manifold rail VABM- ... -S- ... , for in-line valves (manifold assembly) | | | | |
|  | - | - | Valve size M3, M5, M7, G1/8, G1/4 | vabm |
| Manifold rail VABM, for sub-base valves | | | | |
|  | - | 10AW | Connection size M3 | vabm |
| | - | 10W | Connection size M5 | |
| | - | 10HW | Connection size M7 | |
| | - | 14W | Connection size G1/8 | |
| | - | 18W | Connection size G1/4 | |

Solenoid valves VUVG










Overview of valve functions



| Valve | Valve code | Description | Valve terminal/ position function order code | Size | | | |
|--------------------------------------------------------------------------------|------------|-------------------------------------------|----------------------------------------------------|------|-------|------|------|
| | | | | M3 | M5/M7 | G1/8 | G1/4 |
| 2x3/2-way valve, normally closed, pneumatic spring | | | | | | | |
| | T32C-A | In-line valve, internal pilot air supply | K | | | | |
| | | In-line valve, external pilot air supply | | - | ■ | ■ | ■ |
| | | Sub-base valve, external pilot air supply | | | | | |
| 2x3/2-way valve, normally open, pneumatic spring | | | | | | | |
| | T32U-A | In-line valve, internal pilot air supply | N | | | | |
| | | In-line valve, external pilot air supply | | - | ■ | ■ | ■ |
| | | Sub-base valve, external pilot air supply | | | | | |
| 2x3/2-way valve, 1x normally open, 1x normally closed, pneumatic spring | | | | | | | |
| | T32H-A | In-line valve, internal pilot air supply | H | | | | |
| | | In-line valve, external pilot air supply | | - | ■ | ■ | ■ |
| | | Sub-base valve, external pilot air supply | | | | | |

Solenoid valves VUVG













Overview of valve functions

| Valve | Valve code | Description | Valve terminal/ position function order code | Size | | | |
|-------------------------------------------------------------------------------------|------------|-------------------------------------------|----------------------------------------------------|------|-------|------|------|
| | | | | M3 | M5/M7 | G1/8 | G1/4 |
| 2x3/2-way valve, normally closed, mechanical spring | | | | | | | |
|  | T32C-M | In-line valve, internal pilot air supply | VK | | | | |
|  | | In-line valve, external pilot air supply | | - | ■ | ■ | ■ |
|  | | Sub-base valve, external pilot air supply | | | | | |
| 2x3/2-way valve, normally open, mechanical spring | | | | | | | |
|  | T32U-M | In-line valve, internal pilot air supply | VN | | | | |
|  | | In-line valve, external pilot air supply | | - | ■ | ■ | ■ |
|  | | Sub-base valve, external pilot air supply | | | | | |
| 2x3/2-way valve, 1x normally open, 1x normally closed, mechanical spring | | | | | | | |
|  | T32H-M | In-line valve, internal pilot air supply | VH | | | | |
|  | | In-line valve, external pilot air supply | | - | ■ | ■ | ■ |
|  | | Sub-base valve, external pilot air supply | | | | | |

Solenoid valves VUVG

Overview of valve functions

FESTO

| Valve | Valve code | Description | Valve terminal/ position function order code | Size | | | |
|-------------------------------------------------------------------------------------|------------|-------------------------------------------|----------------------------------------------------|------|-------|------|------|
| | | | | M3 | M5/M7 | G1/8 | G1/4 |
| 5/2-way double solenoid valve | | | | | | | |
|  | B52 | In-line valve, internal pilot air supply | J | | | | |
|  | | In-line valve, external pilot air supply | | ■ | ■ | ■ | ■ |
|  | | Sub-base valve, external pilot air supply | | | | | |
| 5/2-way single solenoid valve, pneumatic spring | | | | | | | |
|  | M52-A | In-line valve, internal pilot air supply | M | | | | |
|  | | In-line valve, external pilot air supply | | - | - | ■ | - |
|  | | Sub-base valve, external pilot air supply | | | | | |
| 5/2-way single solenoid valve, mechanical spring | | | | | | | |
|  | M52-M | In-line valve, internal pilot air supply | A | | | | |
|  | | In-line valve, external pilot air supply | | ■ | ■ | ■ | ■ |
|  | | Sub-base valve, external pilot air supply | | | | | |
| 5/2-way single solenoid valve, pneumatic/mechanical spring | | | | | | | |
|  | M52-R | In-line valve, internal pilot air supply | P | | | | |
|  | | In-line valve, external pilot air supply | | ■ | ■ | - | ■ |
|  | | Sub-base valve, external pilot air supply | | | | | |

Solenoid valves VUVG


Overview of valve functions

| Valve | Valve type code | Description | Valve terminal/ position function order code | Size | | | |
|------------------------------------------------|-----------------|-------------------------------------------|----------------------------------------------|------|-------|------|------|
| | | | | M3 | M5/M7 | G1/8 | G1/4 |
| 5/3-way valve, mid-position closed | | | | | | | |
| | P53C | In-line valve, internal pilot air supply | G | | | | |
| | | In-line valve, external pilot air supply | | ■ | ■ | ■ | ■ |
| | | Sub-base valve, external pilot air supply | | | | | |
| 5/3-way valve, mid-position pressurised | | | | | | | |
| | P53U | In-line valve, internal pilot air supply | B | | | | |
| | | In-line valve, external pilot air supply | | ■ | ■ | ■ | ■ |
| | | Sub-base valve, external pilot air supply | | | | | |
| 5/3-way valve, mid-position exhausted | | | | | | | |
| | P53E | In-line valve, internal pilot air supply | E | | | | |
| | | In-line valve, external pilot air supply | | ■ | ■ | ■ | ■ |
| | | Sub-base valve, external pilot air supply | | | | | |

Solenoid valves VUVG

Sample system overview – VUVG-L10 and VUVG-S10, in-line valves M5/M7

Manifold assembly




| Manifold assembly and accessories | | | | |
|-----------------------------------|--------------------------|----------------------|-------------------------------------------------------------------------------|------------|
| | Type | Brief description | → Page/Internet | |
| 1 | Manifold rail | VABM-L1-10S-G18-... | For 2 to 10, 12, 14 and 16 valve positions | 28 |
| 2 | Solenoid valve | VUVG- ... | In-line valve, 5/2-way single solenoid | 22 |
| 3 | Solenoid valve | VUVG- ... | In-line valve, 2x3/2-way, 5/2-way double solenoid and 5/3-way valve | 22 |
| 4 | Blanking plate | VABB-L1-10-S | For covering an unused valve position | 28 |
| 5 | Supply plate | VABF-L1-10-P3A4- ... | For air supply port 1 and outlet port 3 and 5 | 28 |
| 6 | H-rail | NRH-35-2000 | For mounting the valve manifold | 65 |
| 7 | H-rail mounting | VAME-T-M4 | 2 pieces for fitting the valve manifold on an H-rail | 65 |
| 8 | Separator | VABD-... | For creating pressure zones | 28 |
| 9 | Plug socket with cable | NEBV-H1G2-...-LE2 | For E-box H2 and H3 | 63 |
| 10 | Push-in fitting | QS... | Push-in fitting for outlet port 2 and 4 | quick star |
| 11 | Push-in fitting | QS... | Push-in fitting for air supply port 1 | quick star |
| 12 | Silencer | U... | For outlet port 3 and 5 | 64 |
| 13 | Cover cap | VMPA-HB...-B | For manual override | 65 |
| 14 | Inscription label holder | ASLR-D | For labelling the valves, covering the mounting screw and the manual override | 65 |

Solenoid valves VUVG

Sample system overview – VUVG-B10, sub-base valves

Manifold assembly



| Manifold assembly and accessories | | | | |
|-----------------------------------|--------------------------|-------------------------|-------------------------------------------------------------------------------|------------|
| | Type | Brief description | → Page/Internet | |
| 1 | Manifold rail | VABM-L1-10 ...-G18- ... | For 2 to 10, 12, 14 and 16 valve positions | 48 |
| 2 | Solenoid valve | VUVG- ... | Sub-base valve, 5/2-way single solenoid | 44 |
| 3 | Solenoid valve | VUVG- ... | Sub-base valve, 2x3/2-way, 5/2-way double solenoid and 5/3-way valve | 44 |
| 4 | Blanking plate | VABB-L1-10-W | For covering an unused valve position | 48 |
| 5 | Supply plate | VABF-L1-10-P3A4- ... | For air supply port 1 and outlet port 3 and 5 | 48 |
| 6 | H-rail | NRH-35-2000 | For mounting the valve manifold | 65 |
| 7 | H-rail mounting | VAME-T-M4 | 2 pieces for fitting the valve manifold on an H-rail | 65 |
| 8 | Separator | VABD- ... | For creating pressure zones | 48 |
| 9 | Plug socket with cable | NEBV-H1G2-KN-...-LE2 | For E-box H2 and H3 | 63 |
| 10 | Push-in fitting | QS... | Push-in fitting for outlet port 2 and 4 | quick star |
| 11 | Push-in fitting | QS... | Push-in fitting for air supply port 1 | quick star |
| 12 | Silencer | U... | For outlet port 3 and 5 | 64 |
| 13 | Push-in fitting | QS... | Push-in fitting for pilot air supply port 12/14 | quick star |
| 14 | Silencer | U... | Silencer for pilot air outlet 82/84 | 64 |
| 15 | Cover cap | VMPA-HB...-B | For manual override | 65 |
| 16 | Inscription label holder | ASLR-D | For labelling the valves, covering the mounting screw and the manual override | 65 |

Solenoid valves VUVG-L10A and VUVG-S10A, in-line valves M3

Technical data

Function
 5/2-way, single solenoid
 5/2-way, double solenoid
 5/3C, 5/3U, 5/3E

Circuit symbol → page 10

-  - Width 10 mm
-  - Flow rate
90 ... 100 l/min
-  - Voltage
5, 12 and 24 V DC



| General technical data | | | | | | |
|------------------------------------|----------------------------------------------------------------|-----------------|------------|-----------------|-----------------|-----------------|
| Valve function | M52-R | B52 | M52-M | P53 | | |
| Normal position | - | - | - | C ¹⁾ | U ²⁾ | E ³⁾ |
| Stable position | Monostable | Bistable | Monostable | Monostable | | |
| Pneumatic spring reset method | Yes ⁵⁾ | - | No | No | | |
| Mechanical spring reset method | Yes ⁵⁾ | - | Yes | Yes | | |
| Vacuum operation at port 1 | Only with external pilot air supply | | | | | |
| Design | Piston spool valve | | | | | |
| Sealing principle | Soft | | | | | |
| Actuation type | Electric | | | | | |
| Type of control | Piloted | | | | | |
| Pilot air supply | Internal or external | | | | | |
| Exhaust function | With flow control | | | | | |
| Manual override | Choice of non-detenting, detenting or covered | | | | | |
| Type of mounting | Optionally via through-holes ⁷⁾ or on manifold rail | | | | | |
| Mounting position | Any | | | | | |
| Nominal size [mm] | 2 | | 1.4 | 2 | | |
| Standard nominal flow rate [l/min] | 100 | | 80 | 90 | | |
| Flow rate on manifold rail [l/min] | 100 | | 80 | 90 | | |
| Switching time on/off [ms] | 7/15 | - | 7/21 | 8/25 | | |
| Changeover time [ms] | - | 5 | - | 14 | | |
| Width [mm] | 10 | | | | | |
| Connection | 1, 2, 3, 4, 5; 14 | | M3 | | | |
| Product weight [g] | 38 | 49 | 37 | | | |
| Corrosion resistance class | CRC | 2 ⁶⁾ | | | | |

1) C = Normally closed
 2) U = Normally open
 3) E = Normally exhausted
 5) Combined reset method
 6) Corrosion resistance class 2 according to Festo standard 940 070
 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
 7) If several valves are to be screwed together via the through-holes to form a block, a minimum gap of 0.3 mm must be ensured by placing spacer discs between them.

Solenoid valves VUVG-L10A and VUVG-S10A, in-line valves M3

Technical data

| Operating and environmental conditions | | | | | |
|----------------------------------------|----------------|---------------------------------------------------------|-----------|---------------------|------------|
| Valve function | | M52-R ²⁾ | B52 | M52-M ³⁾ | P53 |
| Operating medium | | Compressed air in accordance with ISO 8573-2010 [7:4:4] | | | |
| Operating pressure | Internal [bar] | 2.5 ... 8 | 1.5 ... 8 | 3 ... 8 | 3 ... 8 |
| | External [bar] | -0.9 ... 10 | | | -0.9 ... 8 |
| Pilot pressure ⁴⁾ [bar] | | 2.5 ... 8 | 1.5 ... 8 | 3 ... 8 | |
| Ambient temperature [°C] | | -5 ... +50, -5 ... +60 with holding current reduction | | | |
| Temperature of medium [°C] | | -5 ... +50, -5 ... +60 with holding current reduction | | | |

2) Mixed, pneumatic/mechanical spring

3) Mechanical spring

4) Minimum pilot pressure 50% of operating pressure

| Electrical data | |
|------------------------------|---------------------------------------------------|
| Electrical connection | Via E-box |
| Operating voltage [V DC] | 5, 12 and 24 ±10% |
| Power [W] | 1, reduced to 0.35 with holding current reduction |
| Duty cycle [%] | 100 |
| Protection class to EN 60529 | IP40 (with plug socket), IP65 (with M8) |

| Information on materials | |
|--------------------------|-------------------------|
| Housing | Wrought aluminium alloy |
| Seals | HNBR, NBR |
| Note on materials | RoHS-compliant |

Solenoid valves VUVG-L10A and VUVG-S10A, in-line valves M3

Technical data

Dimensions Download CAD data → www.festo.com

5/2-way and 5/3-way valve





- - Note
 More dimensions
 E-boxes
 → page 61

1 Horizontal electrical connection
 2 Manual override
 3 Port for external pilot air supply

| Type | B1 | B2 | B3 | D1 | D2 | H1 | H2 | L1 | L2 | L3 | L4 | L5 |
|-----------------------|------|------|------|----|------|------|-------|------|------|------|-------|-------|
| VUVG-L-10 -...-M3 ... | 10.2 | 3.6 | 2.83 | M3 | 3.2 | 32.5 | 4.4 | 74.3 | 69.3 | 8 | 18.5 | 25.4 |
| VUVG-S-10 -...-M3 ... | L6 | L7 | L8 | L9 | L10 | L11 | L12 | L13 | L14 | L15 | L16 | L17 |
| | 4.85 | 6.15 | 34.9 | 7 | 11.9 | 7.3 | 15.25 | 28.5 | 6.7 | 8.54 | 57.06 | 54.56 |

Solenoid valves VUVG-L10A and VUVG-S10A, in-line valves

Order code

| | | | | | | |
|-------------------------------------------------------------------------------------|--------------------------|-----|---|---|------|---|
| VUVG | - | 10A | - | - | - | - |
| Valve design | | | | | | |
|  | | L | | | | |
| In-line, individual valve | | | | | | |
|  | | S | | | | |
| In-line, manifold valve incl. seal and screws | | | | | | |
| Width | | | | | | |
| 10 mm | | 10A | | | | |
| Valve functions | | | | | | |
|  | | | | | M52 | |
|  | | | | | B52 | |
|  | | | | | P53C | |
|  | | | | | P53U | |
|  | | | | | P53E | |
| Reset method | | | | | | |
| Mech. spring for M52 | | | | | M | |
| Pneu./mech. spring for M52 | | | | | R | |
| With B52 and P53 | | | | | - | |
| Pilot air supply | | | | | | |
| Internal | | | | | - | |
| External | | | | | Z | |
| Manual override | | | | | | |
|  | Non-detenting | | | | H | |
|  | Covered | | | | S | |
| - | Non-detenting, detenting | | | | T | |

| | | | | | | | |
|-------------------------------|----------------------------------------------------------------|--|--|--|--|---|---------------------------------------------------------------------------------------|
| | | | | | | L | - |
| Connecting cables | | | | | | | |
| W1...4 | Not sheathed | | | | | |  |
| C1...4 | Sheathed | | | | | | for H |
| WS1...4 | Not sheathed | | | | | |  |
| S1...4 | Sheathed | | | | | | for S |
| N1...4 | M8x1, 4-pin | | | | | |  |
| N5...8 | M8x1, 4-pin | | | | | |  |
| Display | | | | | | | |
| L | LED | | | | | | |
| Protective circuit | | | | | | | |
| - | Without holding current reduction (HCR) | | | | | | |
| R | With holding current reduction (HCR) | | | | | | |
| E-box | | | | | | | |
| H2 | Connection pattern H, horizontal plug | | | | | |  |
| H3 | Connection pattern H, vertical plug | | | | | |  |
| S2 | Connection pattern S, horizontal plug | | | | | |  |
| S3 | Connection pattern S, vertical plug | | | | | |  |
| L1...4 | With 2x flying leads L: 1 = 0.5 m, 2 = 1 m, 3 = 2.5 m, 4 = 5 m | | | | | |  |
| K6...9 | Cable: K6 = 0.5 m, K7 = 1 m, K8 = 2.5 m, K9 = 5 m | | | | | |  |
| R1 | Individual plug M8, 4-pin | | | | | |  |
| R8 | Individual plug M8, 3-pin | | | | | |  |
| P3 | Without E-box | | | | | |  |
| Operating voltage | | | | | | | |
| 1 | 24 V DC | | | | | | |
| 5 | 12 V DC | | | | | | |
| 4 | 5 V DC | | | | | | |
| Exhausting with VUVG-L | | | | | | | |
| QN | QS if QS ³⁾ | | | | | | |
| U | Silencer | | | | | | |
| - | G ¹ / ₈ | | | | | | |
| Pneumatic connection | | | | | | | |
| M3 | Thread M3 | | | | | | |
| T18 | Push-in connector 1/8" | | | | | | |
| T532 | Push-in connector 3/32" | | | | | | |
| Q3 | Push-in connector 3 mm/M3 | | | | | | |
| Q4 | Push-in connector 4 mm/M3 | | | | | | |

Solenoid valves VUVG-S10A, in-line valves M3

Manifold assembly




In-line valves for manifold assembly



Dimensions

Download CAD data → www.festo.com



Note
More dimensions
E-boxes
→ page 59

1 Blanking plate VABB-L1-10A-S

2 Supply plate
VABF-L1-10A-P3A4-M3

3 Single solenoid
valve without
E-box

4 Double solenoid valve without
E-box

5 Solenoid valve, vertical
electrical connection


6 H-rail mounting (two M4x16
screws to DIN 912 are required
for mounting)

| Type | | | | | | | | | | | | |
|-----------------------|-------|------|------|------|------|-----|------|-----|------|------|------|-----|
| VUVG-S10A -...-M3 ... | B1 | B2 | B3 | B4 | B5 | B6 | B7 | B8 | B9 | B10 | B11 | D1 |
| | 85.3 | 62.6 | 29.7 | 18.7 | 7.7 | 3 | 40.3 | 6.8 | 24.2 | 46.7 | 38.6 | M5 |
| | D2 | H1 | H2 | H3 | H4 | H5 | H6 | L3 | L5 | L6 | L7 | L8 |
| | ∅ 4.5 | 43.8 | 10 | 5.5 | 16.2 | 6.8 | 20.3 | 7 | 12.5 | 10.3 | 10.5 | 3.5 |
| | L9 | | | | | | | | | | | |
| | 14 | | | | | | | | | | | |

| Valve positions | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 12 | 14 | 16 |
|-----------------|------|----|------|----|------|----|-------|-----|-------|-------|-------|-------|
| L1 [mm] | 42.5 | 53 | 63.5 | 74 | 84.5 | 95 | 105.5 | 116 | 126.5 | 147.5 | 168.5 | 189.5 |
| L2 [mm] | 28.5 | 39 | 49.5 | 60 | 70.5 | 81 | 91.5 | 102 | 112.5 | 133.5 | 154.5 | 175.5 |
| L4 [mm] | 35.5 | 46 | 56.5 | 67 | 77.5 | 88 | 98.5 | 109 | 119.5 | 140.5 | 161.5 | 182.5 |
| VABM weight [g] | 26 | 34 | 42 | 50 | 58 | 66 | 74 | 82 | 90 | 106 | 122 | 138 |

Solenoid valves VUVG-S10A, in-line valves M3

Ordering data

| Technical data – Manifold rails | | | | | | | |
|-----------------------------------------------------------------------------------|------------|-----------------|-------------------------|--------------------|------------------------------------------|--------|------|
| | Connection | CRC | Material ²⁾ | Operating pressure | Max. tightening torque for assembly [Nm] | | |
| | 1, 3, 5 | | | [bar] | Valve | H-rail | Wall |
|  | M5 | 2 ¹⁾ | Wrought aluminium alloy | -0.9 ... 10 | 0.45 | 1.5 | 3 |

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 2) Note on materials: RoHS-compliant

Order code – Manifold rails

| | | | | | | | | | |
|----------------------------------|---|-------------|---|------------|----------|---|-----------|---------------------------|--|
| VABM | - | L1 | - | 10A | S | - | M5 | - | |
| Manifold assembly parts | | | | | | | | Number of valve positions | |
| Manifold rail | | VABM | | | | | | 2 to 10, 12, 14 and 16 | |
| Valve series | | | | | | | | Ports 1, 3, 5 | |
| VUVG | | L1 | | | | | | M5 M5 | |
| Valve width | | | | | | | | | |
| 10 mm | | | | 10A | | | | | |
| Manifold rail with ports 1, 3, 5 | | | | | | | | | |
| For M3 in-line valves | | | | S | | | | | |

Ordering data – Accessories

| | | | Type |
|-------------------------------------------------------------------------------------|-----------------------------------------|------------------------------|---------------------------------|
| Blanking plate | | | Technical data → Internet: vabb |
|  | For manifold rail for M3 in-line valves | Incl. screws and seal | VABB-L1-10A |
| Separator | | | Technical data → Internet: vabd |
|  | For manifold rail for M3 in-line valves | Separator for pressure zones | VABD-4.2-B |
| Supply plate | | | Technical data → Internet: vabf |
|  | For manifold rail for M3 in-line valves | Incl. screws and seal | VABF-L1-10A-P3A4-M5 |
| Seals for in-line valves | | | Technical data → Internet: vabd |
|  | M3 | 10 seals and 20 screws | VABD-L1-10AX-S-M3 |

Solenoid valves VUVG-L10 and VUVG-S10, in-line valves M5

FESTO

Technical data

Function

2x3/2C, 2x3/2U, 2x3/2H

5/2-way, single solenoid

5/2-way, double solenoid


5/3C, 5/3U, 5/3E

Circuit symbol → page 10

-  - Width 10 mm

-  - Flow rate
150 ... 220 l/min

-  - Voltage
5, 12 and 24 V DC



| General technical data | | | | | | | | | | | | | |
|------------------------------------|----------------------------------------------------------------|-----------------|-----------------|-------------------------------------|-----------------|-----------------|-------------------|----------|------------|-----------------|-----------------|-----------------|-------|
| Valve function | T32-A | | | T32-M | | | M52-R | B52 | M52-M | P53 | | | |
| Normal position | C ¹⁾ | U ²⁾ | H ⁴⁾ | C ¹⁾ | U ²⁾ | H ⁴⁾ | - | - | - | C ¹⁾ | U ²⁾ | E ³⁾ | |
| Stable position | Monostable | | | | | | | Bistable | Monostable | Monostable | | | |
| Pneumatic spring reset method | Yes | | | No | | | Yes ⁵⁾ | - | No | No | | | |
| Mechanical spring reset method | No | | | Yes | | | Yes ⁵⁾ | - | Yes | Yes | | | |
| Vacuum operation at port 1 | No | | | Only with external pilot air supply | | | | | | | | | |
| Design | Piston spool valve | | | | | | | | | | | | |
| Sealing principle | Soft | | | | | | | | | | | | |
| Actuation type | Electric | | | | | | | | | | | | |
| Type of control | Piloted | | | | | | | | | | | | |
| Pilot air supply | Internal or external | | | | | | | | | | | | |
| Exhaust function | With flow control | | | | | | | | | | | | |
| Manual override | Choice of non-detenting, detenting or covered | | | | | | | | | | | | |
| Type of mounting | Optionally via through-holes ⁷⁾ or on manifold rail | | | | | | | | | | | | |
| Mounting position | Any | | | | | | | | | | | | |
| Nominal size [mm] | 2.7 | | | 1.9 | | 1.8 | | 3.2 | | 2.2 | | 3.2 | |
| Standard nominal flow rate [l/min] | 150 | | | 135 | | 125 | | 220 | | 190 | | 210 | |
| Flow rate on manifold rail [l/min] | 150 | | | 135 | | 125 | | 220 | | 190 | | 210 | |
| Switching time on/off [ms] | 6/16 | | | 8/11 | | | | 7/19 | | - | | 8/24 | 10/30 |
| Changeover time [ms] | - | | | | | | | 7 | | - | | 16 | |
| Width [mm] | 10 | | | | | | | | | | | | |
| Connection | 1, 2, 3, 4, 5 | | | M5 | | | | | | | | | |
| | 12, 14 | | | M3 | | | | | | | | | |
| Product weight [g] | 55 | | | 54 | | | 45 | | 55 | | 44 | | 55 |
| Corrosion resistance class | CRC | | | 2 ⁶⁾ | | | | | | | | | |

1) C = Normally closed

2) U = Normally open

3) E = Normally exhausted

4) H = 2x3/2-way valve in one housing with 1x normally closed and 1x normally open

5) Combined reset method

6) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

7) If several valves are to be screwed together via the through-holes to form a block, a minimum gap of 0.3 mm must be ensured by placing spacer discs between them.


Solenoid valves VUVG-L10 and VUVG-S10, in-line valves M7

Technical data

Function
 2x3/2C, 2x3/2U, 2x3/2H
 5/2-way, single solenoid
 5/2-way, double solenoid
 5/3C, 5/3U, 5/3E

Circuit symbol → page 10

-  - Width 10 mm
-  - Flow rate
190 ... 380 l/min
-  - Voltage
5, 12 and 24 V DC



| General technical data | | | | | | | | | | | | |
|------------------------------------|----------------------------------------------------------------|-----------------|-----------------|-------------------------------------|-----------------|-----------------|-------------------|----------|------------|-----------------|-----------------|-----------------|
| Valve function | T32-A | | | T32-M | | | M52-R | B52 | M52-M | P53 | | |
| Normal position | C ¹⁾ | U ²⁾ | H ⁴⁾ | C ¹⁾ | U ²⁾ | H ⁴⁾ | - | - | - | C ¹⁾ | U ²⁾ | E ³⁾ |
| Stable position | Monostable | | | | | | | Bistable | Monostable | Monostable | | |
| Pneumatic spring reset method | Yes | | | No | | | Yes ⁵⁾ | - | No | No | | |
| Mechanical spring reset method | No | | | Yes | | | Yes ⁵⁾ | - | Yes | Yes | | |
| Vacuum operation at port 1 | No | | | Only with external pilot air supply | | | | | | | | |
| Design | Piston spool valve | | | | | | | | | | | |
| Sealing principle | Soft | | | | | | | | | | | |
| Actuation type | Electric | | | | | | | | | | | |
| Type of control | Piloted | | | | | | | | | | | |
| Pilot air supply | Internal or external | | | | | | | | | | | |
| Exhaust function | With flow control | | | | | | | | | | | |
| Manual override | Choice of non-detenting, detenting or covered | | | | | | | | | | | |
| Type of mounting | Optionally via through-holes ⁷⁾ or on manifold rail | | | | | | | | | | | |
| Mounting position | Any | | | | | | | | | | | |
| Nominal size [mm] | 2.7 | 2.0 | 1.9 | 1.9 | 4.0 | | | 2.8 | 3.5 | | | |
| Standard nominal flow rate [l/min] | 190 | 150 | 140 | 140 | 380 | | | 320 | 320 | | | |
| Flow rate on manifold rail [l/min] | 170 | 140 | 130 | 130 | 340 | | | 290 | 300 | | | |
| Switching time on/off [ms] | 6/16 | | 8/11 | | | 7/19 | - | 8/24 | 10/30 | | | |
| Changeover time [ms] | - | | | | | | | 7 | 16 | | | |
| Width [mm] | 10 | | | | | | | | | | | |
| Connection | 1, 2, 3, 4, 5 | | | M7 | | | | | | | | |
| | 12, 14 | | | M3 | | | | | | | | |
| Product weight [g] | 55 | | | 54 | | | 45 | 55 | 44 | 55 | | |
| Corrosion resistance class | CRC | | | 2 ⁶⁾ | | | | | | | | |

- 1) C = Normally closed
- 2) U = Normally open
- 3) E = Normally exhausted
- 4) H=2x3/2-way valve in one housing with 1x normally closed and 1x normally open
- 5) Combined reset method
- 6) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 7) If several valves are to be screwed together via the through-holes to form a block, a minimum gap of 0.3 mm must be ensured by placing spacer discs between them.

Solenoid valves VUVG-L10 and VUVG-S10, in-line valves M7

Technical data

| Operating and environmental conditions | | | T32-A ¹⁾ | T32-M ³⁾ | M52-R ²⁾ | B52 | M52-M ³⁾ | P53 |
|----------------------------------------|----------|-------|--------------------------------------------------------------------------------|---------------------|---------------------|-----------|---------------------|-------------|
| Valve function | | | | | | | | |
| Operating medium | | | Filtered compressed air, grade of filtration 40 µm, lubricated or unlubricated | | | | | |
| Operating pressure | Internal | [bar] | 1.5 ... 8 | 2.5 ... 8 | 2.5 ... 8 | 1.5 ... 8 | 3 ... 8 | |
| | External | [bar] | 1.5 ... 10 | -0.9 ... 10 | | | -0.9 ... 8 | -0.9 ... 10 |
| Pilot pressure ⁴⁾ | | | [bar] | 1.5 ... 8 | 2 ... 8 | 2.5 ... 8 | 1.5 ... 8 | 3 ... 8 |
| Ambient temperature | | | [°C] -5 ... +50, -5 ... +60 with holding current reduction | | | | | |
| Temperature of medium | | | [°C] -5 ... +50, -5 ... +60 with holding current reduction | | | | | |

- 1) Pneumatic spring
- 2) Mixed, pneumatic/mechanical spring
- 3) Mechanical spring
- 4) Minimum pilot pressure 50% of operating pressure

| Electrical data | |
|------------------------------|-------------------------------------------------------|
| Electrical connection | Via E-box |
| Operating voltage | [V DC] 5, 12, 24 ±10% |
| Power | [W] 1, reduced to 0.35 with holding current reduction |
| Duty cycle | [%] 100 |
| Protection class to EN 60529 | IP40 (with plug socket), IP65 (with M8) |

| Information on materials | |
|--------------------------|-------------------------|
| Housing | Wrought aluminium alloy |
| Seals | HNBR, NBR |
| Note on materials | RoHS-compliant |

Dimensions Download CAD data → www.festo.com

2x3/2-way, 5/2-way and 5/3-way valve

- - Note
More dimensions
E-boxes
→ page 59

1 Vertical electrical connection

2 Horizontal electrical connection

3 Manual override

4 Port for external pilot air supply


| Type | B1 | B2 | D1 | D2 | D3 | H1 | H2 | H3 | L1 | L2 | L3 | L4 |
|----------------------|------|------|----|-----|----|------|-----|-----|------|------|----|----|
| VUVG-L-10 ...-M7 ... | 10.2 | - | M7 | 3.2 | M3 | 32.5 | 3.6 | 4.4 | 86.5 | 81.5 | 8 | 27 |
| VUVG-S-10 ...-M7 ... | L5 | L6 | L7 | L8 | L9 | L10 | L11 | L12 | L13 | L14 | | |
| | 4.85 | 6.15 | 47 | 14 | 11 | 12 | 19 | - | 69.2 | 66.7 | | |

Solenoid valves VUVG-S10, in-line valves M5/M7

Manifold assembly




In-line valves for manifold assembly



Dimensions

Download CAD data → www.festo.com



Note
More dimensions
E-boxes
→ page 59


- 1 Solenoid valve, vertical electrical connection
- 2 Supply plate, ports 1, 3 and 5: M5 or M7
- 3 Blanking plate VABB-L1-10-S
- 4 Vertical pressure supply plate
- 5 Vertical pressure exhaust plate
- 6 H-rail mounting (two M4x20 screws to DIN 912 are required)

| Type | B1 | B2 | B3 | B4 | B5 | B6 | B7 | B8 | B9 | B10 | B11 | B12 |
|----------------------|-----------------|------|------|------|------|------|------|------|------|------|------|------|
| VUVG-S10 -...-M5 ... | 94.3 | 41 | 24.5 | 8 | 52.1 | 16.5 | 16 | 33.7 | 44.6 | 40.7 | 36.7 | 14.4 |
| | D1 | D2 | D5 | H1 | H2 | H3 | H4 | H5 | H6 | H7 | H8 | L3 |
| | G $\frac{1}{8}$ | 4.5 | 8 | 80.6 | 16.8 | 9.8 | 64.9 | 49.3 | 17.8 | 18 | 5.9 | 5 |
| | L4 | L5 | L6 | L7 | | | | | | | | |
| | 15 | 10.5 | 10.3 | 2 | | | | | | | | |

| Valve positions | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 12 | 14 | 16 | 22 |
|-----------------|------|----|------|-----|------|-----|-------|-----|-------|-------|-------|-------|-------|
| L1 [mm] | 40.5 | 51 | 61.5 | 72 | 82.5 | 93 | 103.5 | 114 | 124.5 | 145.5 | 166.5 | 187.5 | 250.5 |
| L2 [mm] | 30.5 | 41 | 51.5 | 62 | 72.5 | 83 | 93.5 | 104 | 114.5 | 135.5 | 156.5 | 177.5 | 240.5 |
| VABM weight [g] | 63 | 78 | 93 | 108 | 123 | 138 | 153 | 168 | 183 | 213 | 243 | 273 | 363 |

Solenoid valves VUVG-S10, in-line valves M5/M7

Ordering data


| Technical data – Manifold rails | | | | | | | |
|-----------------------------------------------------------------------------------|-----------------|-----------------|-------------------------|--------------------|------------------------------------------|--------|------|
| | Connection | CRC | Material ²⁾ | Operating pressure | Max. tightening torque for assembly [Nm] | | |
| | 1, 3, 5 | | | [bar] | Valve | H-rail | Wall |
|  | G $\frac{1}{8}$ | 2 ¹⁾ | Wrought aluminium alloy | -0.9 ... 10 | 0.45 | 1.5 | 3 |

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 2) Note on materials: RoHS-compliant

Order code – Manifold rails

| | | | | | | | | | |
|----------------------------------|---|-------------|---|-----------|----------|---|------------|-----------------|---------------------------|
| VABM | - | L1 | - | 10 | S | - | G18 | - | |
| Manifold assembly parts | | | | | | | | | Number of valve positions |
| Manifold rail | | VABM | | | | | | | 2 to 10, 12, 14 and 16 |
| Valve series | | | | | | | | | Ports 1, 3, 5 |
| VUVG | | L1 | | | | | G18 | G $\frac{1}{8}$ | |
| Valve width | | | | | | | | | |
| 10 mm | | | | 10 | | | | | |
| Manifold rail with ports 1, 3, 5 | | | | | | | | | |
| For M5 and M7 in-line valves | | | | | S | | | | |

Ordering data – Accessories

| | | | | Type |
|-------------------------------------------------------------------------------------|--------------------------------------------|------------------------------|--|---------------------------------|
| Blanking plate | | | | Technical data → Internet: vabb |
|  | For manifold rail for M5/M7 in-line valves | Incl. screws and seal | | VABB-L1-10-S |
| Separator | | | | Technical data → Internet: vabd |
|  | For manifold rail for M5/M7 in-line valves | Separator for pressure zones | | VABD-8-B |
| Supply plate | | | | Technical data → Internet: vabf |
|  | For manifold rail for M5 in-line valves | Incl. screws and seal | | VABF-L1-10-P3A4-M5 |
| | For manifold rail for M7 in-line valves | | | VABF-L1-10-P3A4-M7 |
| Seals for in-line valves | | | | Technical data → Internet: vabd |
|  | M5 | 10 seals and 20 screws | | VABD-L1-10X-S-M5 |
| | M7 | | | VABD-L1-10X-S-M7 |

Solenoid valves VUVG-L14 and VUVG-S14, in-line valves G1/8

Technical data

Function

2x3/2C, 2x3/2U, 2x3/2H
 5/2-way, single solenoid
 5/2-way, double solenoid
 5/3C, 5/3U, 5/3E

Circuit symbol → page 10

-  - Width 14 mm
-  - Flow rate
580 ... 780 l/min
-  - Voltage
5, 12 and 24 V DC



| General technical data | | | | | | | | | | | | |
|------------------------------------|----------------------------------------------------------------|-----------------|-----------------|-------------------------------------|-----------------|-----------------|-------|----------|------------|-----------------|-----------------|-----------------|
| Valve function | T32-A | | | T32-M | | | M52-A | B52 | M52-M | P53 | | |
| Normal position | C ¹⁾ | U ²⁾ | H ⁴⁾ | C ¹⁾ | U ²⁾ | C ¹⁾ | - | - | - | C ¹⁾ | U ²⁾ | E ³⁾ |
| Stable position | Monostable | | | | | | | Bistable | Monostable | | | |
| Pneumatic spring reset method | Yes | | | No | | | Yes | - | No | No | | |
| Mechanical spring reset method | No | | | Yes | | | No | - | Yes | Yes | | |
| Vacuum operation at port 1 | No | | | Only with external pilot air supply | | | | | | | | |
| Design | Piston spool valve | | | | | | | | | | | |
| Sealing principle | Soft | | | | | | | | | | | |
| Actuation type | Electric | | | | | | | | | | | |
| Type of control | Piloted | | | | | | | | | | | |
| Pilot air supply | Internal or external | | | | | | | | | | | |
| Exhaust function | With flow control | | | | | | | | | | | |
| Manual override | Choice of non-detenting, detenting or covered | | | | | | | | | | | |
| Type of mounting | Optionally via through-holes ⁷⁾ or on manifold rail | | | | | | | | | | | |
| Mounting position | Any | | | | | | | | | | | |
| Nominal size [mm] | 4.6 | | | 4.3 | | | 5.6 | | | | | |
| Standard nominal flow rate [l/min] | 650 | 600 | 650 | 550 | 500 | 500 | 780 | | | 650 | 600 | |
| Flow rate on manifold rail [l/min] | 620 | 580 | | 520 | 480 | 480 | 730 | | | 620 | 580 | |
| Switching time on/off [ms] | 8/23 | | | 11/15 | | | 14/28 | - | 13/40 | 12/40 | | |
| Changeover time [ms] | - | | | - | | | | 8 | - | 20 | | |
| Width [mm] | 14 | | | | | | | | | | | |
| Connection | 1, 2, 3, 4, 5 | | | G1/8 | | | | | | | | |
| | 14 | | | M5 | | | | | | | | |
| Product weight [g] | 89 | | | 80 | | | 78 | 89 | 70 | 89 | | |
| Corrosion resistance class | CRC | | | 2 ⁶⁾ | | | | | | | | |

- 1) C = Normally closed
- 2) U = Normally open
- 3) E = Normally exhausted
- 4) H=2x3/2-way valve in one housing with 1x normally closed and 1x normally open
- 6) Corrosion resistance class 2 according to Festo standard 940 070
 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 7) If several valves are to be screwed together via the through-holes to form a block, a minimum gap of 0.3 mm must be ensured by placing spacer discs between them.

Solenoid valves VUVG-L14 and VUVG-S14, in-line valves G1/8

Technical data

| Operating and environmental conditions | | | T32-A ¹⁾ | T32-M ³⁾ | M52-A ¹⁾ | B52 | M52-M ³⁾ | P53 |
|----------------------------------------|----------|-------|--------------------------------------------------------------------------------|---------------------|---------------------|-----------|---------------------|-------------|
| Valve function | | | | | | | | |
| Operating medium | | | Filtered compressed air, grade of filtration 40 µm, lubricated or unlubricated | | | | | |
| Operating pressure | Internal | [bar] | 1.5 ... 8 | 3 ... 8 | 2.5 ... 8 | 1.5 ... 8 | 3 ... 8 | |
| | External | [bar] | 1.5 ... 10 | -0.9 ... 10 | | | -0.9 ... 8 | -0.9 ... 10 |
| Pilot pressure ⁴⁾ | | [bar] | 1.5 ... 8 | 2 ... 8 | 2.5 ... 8 | 1.5 ... 8 | 3 ... 8 | |
| Ambient temperature | | [°C] | -5 ... +50, -5 ... +60 with holding current reduction | | | | | |
| Temperature of medium | | [°C] | -5 ... +50, -5 ... +60 with holding current reduction | | | | | |

- 1) Pneumatic spring
- 3) Mechanical spring
- 4) Minimum pilot pressure 50% of operating pressure

| Electrical data | |
|------------------------------|-------------------------------------------------------|
| Electrical connection | Via E-box |
| Operating voltage | [V DC] 5, 12 and 24 ±10% |
| Power | [W] 1, reduced to 0.35 with holding current reduction |
| Duty cycle | [%] 100 |
| Protection class to EN 60529 | IP40 (with plug socket), IP65 (with M8) |

| Information on materials | |
|--------------------------|-------------------------|
| Housing | Wrought aluminium alloy |
| Seals | HNBR, NBR |
| Note on materials | RoHS-compliant |

Dimensions Download CAD data → www.festo.com

2x3/2-way, 5/2-way and 5/3-way valve

Note

More dimensions
E-boxes
→ page 59

1

Horizontal electrical connection

2

Manual override

3

Port for external pilot air supply


| Type | B1 | B2 | D1 | D2 | D3 | H1 | H2 | L1 | L2 | L3 | L4 | L5 | L6 |
|------------------------|------|-------|------|-------|-------|-------|------|------|-------|----|----|------|------|
| VUVG-L-14 -...-G18 ... | | | | | | | | | | | | | |
| VUVG-S-14 -...-G18 ... | 14.4 | 2.3 | G1/8 | ∅ 3.2 | M5 | 34.8 | 5.8 | 107 | 102 | 8 | 37 | 4.85 | 6.15 |
| | L7 | L8 | L9 | L10 | L11 | L12 | L13 | L14 | L15 | | | | |
| | 66.5 | 18.35 | 14.9 | 18 | 24.25 | 13.45 | 10.8 | 89.4 | 86.95 | | | | |

Solenoid valves VUVG-S14, in-line valves G1/8

Manifold assembly






In-line valves for manifold assembly



Dimensions

Download CAD data → www.festo.com



Note
More dimensions
E-boxes
→ page 59

- 1 Solenoid valve, vertical electrical connection
- 2 Blanking plate VABB-L1-14
- 3 Supply plate, ports 1, 3 and 5: G1/8
- 4 Vertical pressure supply plate
- 5 Vertical pressure exhaust plate
- 6 H-rail mounting (two M4x25 screws to DIN 912 are required for mounting)


| Type | | | | | | | | | | | | | | |
|-----------------------|-------|------|------|------|------|------|------|------|------|------|------|------|------|-----|
| VUVG-S14 -...-G18 ... | B1 | B2 | B3 | B4 | B5 | B6 | B7 | B8 | B9 | B10 | B11 | B12 | D1 | D2 |
| | 116.6 | 56.6 | 36.5 | 16.4 | 72.9 | 26.5 | 20 | 43.5 | 53.1 | 48.3 | 43.5 | 4.5 | G1/4 | 4.5 |
| | H1 | H2 | H3 | H4 | H5 | H6 | H7 | H8 | L3 | L4 | L5 | L6 | L7 | |
| | 95.3 | 20 | 10.6 | 74.9 | 54.8 | 23.9 | 15.4 | 6.5 | 5 | 17 | 16 | 14.5 | 2 | |

| Valve positions | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 12 | 14 | 16 | 22 |
|-----------------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| L1 [mm] | 50 | 66 | 82 | 98 | 114 | 130 | 146 | 162 | 178 | 210 | 242 | 274 | 306 |
| L2 [mm] | 40 | 56 | 72 | 88 | 104 | 120 | 136 | 152 | 168 | 200 | 232 | 264 | 296 |
| VABM weight [g] | 118 | 159 | 200 | 241 | 282 | 323 | 364 | 405 | 446 | 528 | 610 | 692 | 938 |

1) Grid dimension

Solenoid valves VUVG-S14, in-line valves G1/8

Ordering data


| Technical data – Manifold rails | | | | | | | |
|-----------------------------------------------------------------------------------|------------|-----------------|-------------------------|--------------------|------------------------------------------|--------|------|
| | Connection | CRC | Material ²⁾ | Operating pressure | Max. tightening torque for assembly [Nm] | | |
| | 1, 3, 5 | | | [bar] | Valve | H-rail | Wall |
|  | G1/4 | 2 ¹⁾ | Wrought aluminium alloy | -0.9 ... 10 | 0.65 | 1.5 | 3 |

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 2) Note on materials: RoHS-compliant

Order code – Manifold rails

| | | | | | | | | | |
|----------------------------------|---|-------------|---|-----------|----------|---|------------|---------------------------|--|
| VABM | - | L1 | - | 14 | S | - | G14 | - | |
| Manifold assembly parts | | | | | | | | Number of valve positions | |
| Manifold rail | | VABM | | | | | | 2 to 10, 12, 14 and 16 | |
| Valve series | | | | | | | | Ports 1, 3, 5 | |
| VUVG | | L1 | | | | | | G14 G1/4 | |
| Valve width | | | | | | | | | |
| 14 mm | | | | 14 | | | | | |
| Manifold rail with ports 1, 3, 5 | | | | | | | | | |
| For G1/8 in-line valves | | | | S | | | | | |

Ordering data – Accessories

| | | | Type |
|-------------------------------------------------------------------------------------|-------------------------------------------|------------------------------|---------------------------------|
| Blanking plate | | | Technical data → Internet: vabb |
|  | For manifold rail for G1/8 in-line valves | Incl. screws and seal | VABB-L1-14 |
| Separator | | | Technical data → Internet: vabd |
|  | For manifold rail for G1/8 in-line valves | Separator for pressure zones | VABD-10-B |
| Supply plate | | | Technical data → Internet: vabf |
|  | For manifold rail for G1/8 in-line valves | Incl. screws and seal | VABF-L1-14-P3A4-G18 |
| Seals for in-line valves | | | Technical data → Internet: vabd |
|  | G1/8 | 10 seals and 20 screws | VABD-L1-14X-S-G18 |

Solenoid valves VUVG-L18 and VUVG-S18, in-line valves G1/4

Technical data

Function

2x3/2C, 2x3/2U, 2x3/2H
5/2-way, single solenoid
5/2-way, double solenoid
5/3C, 5/3U, 5/3E

Circuit symbol → page 10

-  - Width 18 mm
-  - Flow rate
1,000 ... 1,380 l/min
-  - Voltage
5, 12 and 24 V DC



| General technical data | | | | | | | | | | | | |
|------------------------------------|--------------------------------------------------|-----------------|-----------------|-------------------------------------|-----------------|-----------------|-------------------|----------|------------|-----------------|-----------------|-----------------|
| Valve function | T32-A | | | T32-M | | | M52-R | B52 | M52-M | P53 | | |
| Normal position | C ¹⁾ | U ²⁾ | H ⁴⁾ | C ¹⁾ | U ²⁾ | C ¹⁾ | - | - | - | C ¹⁾ | U ²⁾ | E ³⁾ |
| Stable position | Monostable | | | | | | | Bistable | Monostable | | | |
| Pneumatic spring reset method | Yes | | | No | | | Yes ⁵⁾ | - | No | No | | |
| Mechanical spring reset method | No | | | Yes | | | Yes ⁵⁾ | - | Yes | Yes | | |
| Vacuum operation at port 1 | No | | | Only with external pilot air supply | | | | | | | | |
| Design | Piston spool valve | | | | | | | | | | | |
| Sealing principle | Soft | | | | | | | | | | | |
| Actuation type | Electric | | | | | | | | | | | |
| Type of control | Piloted | | | | | | | | | | | |
| Pilot air supply | Internal/external | | | | | | | | | | | |
| Exhaust function | With flow control | | | | | | | | | | | |
| Manual override | Choice of non-detenting, detenting or covered | | | | | | | | | | | |
| Type of mounting | Optionally via through-holes or on manifold rail | | | | | | | | | | | |
| Mounting position | Any | | | | | | | | | | | |
| Nominal size [mm] | 5.7 | | | | | | 6.9 | 7.3 | 6.9 | 6.5 | 6.3 | |
| Standard nominal flow rate [l/min] | 1,000 | | | | | | 1,300 | 1,380 | 1,300 | 1,200 | 1,000 | |
| Flow rate on manifold rail | 1,000 | | | | | | 1,300 | 1,380 | 1,300 | 1,200 | 1,000 | |
| Switching time on/off [ms] | 13/27 | | | 15/22 | | | 15/31 | | 10/45 | 15/48 | | |
| Changeover time [ms] | - | | | | | | 11 | | - | 29 | | |
| Width [mm] | 18 | | | | | | | | | | | |
| Connection | 1, 2, 3, 4, 5 | | | G1/4 | | | | | | | | |
| | 12/14 | | | M5 | | | | | | | | |
| Product weight [g] | 164 | | | | | | 154 | 164 | 154 | 160 | | |
| Corrosion resistance class | CRC | | | 2 ⁶⁾ | | | | | | | | |

- 1) C = Normally closed
- 2) U = Normally open
- 3) E = Normally exhausted
- 4) H=2x3/2-way valve in one housing with 1x normally closed and 1x normally open
- 5) Combined reset method
- 6) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 7) If several valves are to be screwed together via the through-holes to form a block, a minimum gap of 0.3 mm must be ensured by placing spacer discs between them.

Solenoid valves VUVG-L18 and VUVG-S18, in-line valves G1/4

FESTO

Technical data

| Operating and environmental conditions | | | | | | |
|----------------------------------------|--------------------------------------------------------------------------------|-------|-------------------------------------------------------|---------------------|---------------------|--------------------------------|
| Valve function | | | T32-A ¹⁾ | T32-M ³⁾ | M52-R ²⁾ | B52, M52-M ³⁾ , P53 |
| Operating medium | Filtered compressed air, grade of filtration 40 µm, lubricated or unlubricated | | | | | |
| Operating pressure | Internal | [bar] | 1.5 ... 8 | 3 ... 8 | 2.5 ... 8 | 1.5 ... 8, 3 ... 8 |
| | External | [bar] | 1.5 ... 10 | -0.9 ... 10 | | |
| Pilot pressure ⁴⁾ | | [bar] | 1.5 ... 8 | 2 ... 8 | 2.5 ... 8 | 1.5 ... 8, 3 ... 8 |
| Ambient temperature | | [°C] | -5 ... +50, -5 ... +60 with holding current reduction | | | |
| Temperature of medium | | [°C] | -5 ... +50, -5 ... +60 with holding current reduction | | | |


- 1) Pneumatic spring
- 2) Mixed, pneumatic/mechanical spring
- 3) Mechanical spring
- 4) Minimum pilot pressure 50% of operating pressure

| Electrical data | |
|------------------------------|-------------------------------------------------------|
| Electrical connection | Via E-box |
| Operating voltage | [V DC] 5, 12 and 24 ±10% |
| Power | [W] 1, reduced to 0.35 with holding current reduction |
| Duty cycle | [%] 100 |
| Protection class to EN 60529 | IP40 (with plug socket), IP65 (with M8) |

| Information on materials | |
|--------------------------|-------------------------|
| Housing | Wrought aluminium alloy |
| Seals | HNBR, NBR |
| Note on materials | RoHS-compliant |

Dimensions Download CAD data → www.festo.com

2x3/2-way, 5/2-way and 5/3-way valve



-  Note
More dimensions
E-boxes
→ page 59


1 Electrical connection
 2 Mounting screw
 3 Port for external pilot air supply

| Type | B1 | B2 | D1 | D2 | D3 | H1 | H2 | H3 | L1 | L2 | L3 | L4 | L5 |
|---------------|------|-----|------|-------|------|------|------|-----|-------|-------|------|-------|-------|
| VUVG-L-18 ... | 18.3 | 4.5 | G1/4 | ∅ 4.2 | M5 | 43.1 | 37.8 | 6.4 | 129.4 | 124.4 | 86.4 | 112.2 | 109.7 |
| VUVG-S-18 ... | | | | | | | | | | | | | |
| | L6 | L7 | L8 | L9 | L10 | L11 | L12 | L13 | | | | | |
| | 86 | 52 | 19.7 | 31.3 | 23.8 | 21.7 | 21.1 | 14 | | | | | |

Solenoid valves VUVG-S18, in-line valves G $\frac{1}{4}$


Manifold assembly

In-line valves for manifold assembly



Dimensions

Download CAD data → www.festo.com



 Note
 More dimensions
 E-boxes
 → page 59


- 1** Ports 1, 3 and 5: G $\frac{3}{8}$ (at both ends)
- 2** Blanking plate VABB-L1-18
- 3** Supply plate, ports 1, 3 and 5: G $\frac{1}{4}$
VABF-L1-18-P3A4-G18
- 4** Double solenoid valve
- 5** Single solenoid valve
- 6** H-rail mounting (two M4x35 screws to DIN 912 are required for mounting)

| Type | B1 | B2 | B3 | B4 | B5 | B6 | B7 | B8 | B9 | D1 |
|-----------------------|-------|-------|------|------|------|------|------|------|----|-----|
| VUVG-S18 -...-G14 ... | 129.4 | 124.4 | 95.6 | 76.8 | 47.8 | 18.8 | 51.7 | 34.8 | 26 | 4.5 |
| | H1 | H2 | H3 | H4 | H5 | H6 | L3 | L4 | L5 | L6 |
| | 72.1 | 29 | 11.5 | 28.4 | 27.6 | 6.5 | 6 | 20.5 | 19 | 1 |

| Valve positions | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 12 | 14 | 16 |
|-----------------|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| L1 [mm] | 61 | 80 | 99 | 118 | 137 | 156 | 175 | 194 | 213 | 251 | 289 | 327 |
| L2 [mm] | 49 | 68 | 87 | 106 | 125 | 144 | 163 | 182 | 201 | 239 | 277 | 315 |
| VABM weight [g] | 118 | 159 | 200 | 241 | 282 | 323 | 364 | 405 | 446 | 528 | 610 | 692 |

Solenoid valves VUVG-S18, in-line valves G1/4

Ordering data


| Technical data – Manifold rails | | | | | | | |
|-----------------------------------------------------------------------------------|------------|-----------------|-------------------------|--------------------|------------------------------------------|--------|------|
| | Connection | CRC | Material ²⁾ | Operating pressure | Max. tightening torque for assembly [Nm] | | |
| | 1, 3, 5 | | | [bar] | Valve | H-rail | Wall |
|  | G3/8 | 2 ¹⁾ | Wrought aluminium alloy | -0.9 ... 10 | | | |

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 2) Note on materials: RoHS-compliant

Order code – Manifold rails

| | | | | | | | | | |
|----------------------------------|---|-------------|---|-----------|----------|---|------------|---|---------------------------|
| VABM | - | L1 | - | 18 | S | - | G38 | - | |
| Manifold assembly parts | | | | | | | | | Number of valve positions |
| Manifold rail | | VABM | | | | | | | 2 to 10, 12, 14 and 16 |
| Valve series | | | | | | | | | Ports 1, 3, 5 |
| VUVG | | L1 | | | | | | | G38 G3/8 |
| Valve width | | | | | | | | | |
| 14 mm | | | | 18 | | | | | |
| Manifold rail with ports 1, 3, 5 | | | | | | | | | |
| For G1/4 in-line valves | | | | | S | | | | |

Ordering data – Accessories

| | | | | Type |
|-------------------------------------------------------------------------------------|-------------------------------------------|------------------------------|--|---------------------------------|
| Blanking plate | | | | Technical data → Internet: vabb |
|  | For manifold rail for G1/4 in-line valves | Incl. screws and seal | | VABB-L1-18 |
| Separator | | | | Technical data → Internet: vabd |
|  | For manifold rail for G1/4 in-line valves | Separator for pressure zones | | VABD-14-B |
| Supply plate | | | | Technical data → Internet: vabf |
|  | For manifold rail for G1/4 in-line valves | Incl. screws and seal | | VABF-L1-18-P3A4-G14 |
| Seals for in-line valves | | | | Technical data → Internet: vabd |
|  | G1/4 | 10 seals and 20 screws | | VABD-L1-18X-S-G14 |

Solenoid valves VUVG-B10A, sub-base valves

Technical data

Function

5/2-way, single solenoid
 5/2-way, double solenoid
 5/3C, 5/3U, 5/3E

Circuit symbol → page 10

-  - Width 10 mm
-  - Flow rate
90 ... 100 l/min
-  - Voltage
5, 12 and 24 V DC



| General technical data | | | | | | |
|--------------------------------|--------------------------------------------------|---------------------|------------|-----------------|-----------------|-----------------|
| Valve function | M52-R | B52 | M52-M | P53 | | |
| Normal position | - | - | - | C ¹⁾ | U ²⁾ | E ³⁾ |
| Stable position | Monostable | Bistable | Monostable | Monostable | | |
| Pneumatic spring reset method | Yes ⁵⁾ | - | No | No | | |
| Mechanical spring reset method | Yes ⁵⁾ | - | Yes | Yes | | |
| Vacuum operation at port 1 | Only with external pilot air supply | | | | | |
| Design | Piston spool valve | | | | | |
| Sealing principle | Soft | | | | | |
| Actuation type | Electric | | | | | |
| Type of control | Piloted | | | | | |
| Pilot air supply | External, internal; can be selected via sub-base | | | | | |
| Exhaust function | With flow control | | | | | |
| Manual override | Choice of non-detenting, detenting or covered | | | | | |
| Type of mounting | On manifold rail | | | | | |
| Mounting position | Any | | | | | |
| Nominal size | [mm] | 2 | 1.4 | 2 | | |
| Standard nominal flow rate | [l/min] | 100 | 80 | 90 | | |
| Flow rate on manifold rail M3 | [l/min] | 100 | 80 | 90 | | |
| Switching time on/off | [ms] | 7/15 | - | 7/21 | 8/25 | |
| Changeover time | [ms] | - | 5 | - | 14 | |
| Width | [mm] | 10 | | | | |
| Connection | 1, 3, 5 | M7 in manifold rail | | | | |
| | 2, 4 | M5 in manifold rail | | | | |
| | 12/14, 82/84 | M5 in manifold rail | | | | |
| Product weight | [g] | 38 | 49 | 37 | 49 | |
| Corrosion resistance class | CRC | 2 ⁶⁾ | | | | |

1) C = Normally closed
 2) U = Normally open
 3) E = Normally exhausted
 5) Combined reset method
 6) Corrosion resistance class 2 according to Festo standard 940 070
 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Solenoid valves VUVG-B10A, sub-base valves

Technical data

| Operating and environmental conditions | | | | | |
|----------------------------------------|----------------|--------------------------------------------------------------------------------|-----------|---------------------|-------------|
| Valve function | | M52-R ²⁾ | B52 | M52-M ³⁾ | P53 |
| Operating medium | | Filtered compressed air, grade of filtration 40 µm, lubricated or unlubricated | | | |
| Operating pressure | Internal [bar] | 2.5 ... 8 | 1.5 ... 8 | 3 ... 8 | |
| | External [bar] | -0.9 ... 10 | | -0.9 ... 8 | -0.9 ... 10 |
| Pilot pressure ⁴⁾ [bar] | | 2.5 ... 8 | 1.5 ... 8 | 2 ... 8 | 3 ... 8 |
| Ambient temperature [°C] | | -5 ... +50, -5 ... +60 with holding current reduction | | | |
| Temperature of medium [°C] | | -5 ... +50, -5 ... +60 with holding current reduction | | | |

- 2) Mixed, pneumatic/mechanical spring
- 3) Mechanical spring
- 4) Minimum pilot pressure 50% of operating pressure

| Electrical data | |
|------------------------------|---------------------------------------------------|
| Electrical connection | Via E-box |
| Operating voltage [V DC] | 5, 12 and 24 ±10% |
| Power [W] | 1, reduced to 0.35 with holding current reduction |
| Duty cycle [%] | 100 |
| Protection class to EN 60529 | IP40 (with plug socket), IP65 (with M8) |

| Information on materials | |
|--------------------------|-------------------------|
| Housing | Wrought aluminium alloy |
| Seals | HNBR, NBR |
| Note on materials | RoHS-compliant |

Dimensions Download CAD data → www.festo.com

5/2-way and 5/3-way valve







1 Vertical electrical connection 2 Manual override

- - Note
 More dimensions
 E-boxes
 → page 59

| Type | B1 | H1 | L1 | L2 | L3 | L4 | L5 | L6 | L7 |
|----------------------|------|------|------|------|----|------|------|------|------|
| VUVG-B10A -...-F ... | 10.2 | 32.5 | 73.9 | 68.9 | 8 | 4.85 | 6.15 | 56.9 | 54.4 |

Solenoid valves VUVG-B10A, sub-base valves

Order code

| | | | | | | |
|---------------------------------------------------------------------------------------------------------------------------------------------|---|-----|---|---|---|------|
| VUVG | - | 10A | - | - | - | - |
| Valve design | | | | | | |
|  <p>Sub-base, manifold valve incl. seal and screws</p> | | | | | | B |
| Width | | | | | | |
| 10 mm | | | | | | 10A |
| Valve functions | | | | | | |
|  | | | | | | M52 |
|  | | | | | | B52 |
|  | | | | | | P53C |
|  | | | | | | P53U |
|  | | | | | | P53E |
| Reset method | | | | | | |
| Mech. spring for M52 | | | | | | M |
| Pneu./mech. spring for M52 | | | | | | R |
| With B52 and P53 | | | | | | - |
| Pilot air supply | | | | | | |
| External | | | | | | Z |
| Manual override | | | | | | |
|  Non-detenting | | | | | | H |
|  Covered | | | | | | S |
| - Non-detenting, detenting | | | | | | T |


| | | | |
|-------------------------------------------|----------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|
| | | L | - |
| Connecting cables | | | |
| W1...4 | Not sheathed |  | |
| C1...4 | Sheathed | | for H |
| WS1...4 | Not sheathed |  | |
| S1...4 | Sheathed | | for S |
| N1...4 | M8x1, 4-pin |  | |
| N5...8 | M8x1, 4-pin |  | |
| Display | | | |
| L LED | | | |
| Protective circuit | | | |
| - Without holding current reduction (HCR) | | | |
| R With holding current reduction (HCR) | | | |
| E-box | | | |
| H2 | Connection pattern H, horizontal plug | |  |
| H3 | Connection pattern H, vertical plug | |  |
| S2 | Connection pattern S, horizontal plug | |  |
| S3 | Connection pattern S, vertical plug | |  |
| L1...4 | With 2x flying leads L: 1 = 0.5 m, 2 = 1 m, 3 = 2.5 m, 4 = 5 m | |  |
| K6...9 | Cable: K6 = 0.5 m, K7 = 1 m, K8 = 2.5 m, K9 = 5 m | |  |
| R1 | Individual plug M8, 4-pin | |  |
| R8 | Individual plug M8, 3-pin | |  |
| P3 | Without E-box | |  |
| Operating voltage | | | |
| 1 24 V DC | | | |
| 5 12 V DC | | | |
| 4 5 V DC | | | |
| Pneumatic connection | | | |
| F In the manifold rail | | | |

Solenoid valves VUVG-B10A, sub-base valves

Manifold assembly




Sub-base valve for manifold assembly
M5 connection



Dimensions

Download CAD data → www.festo.com



Note
More dimensions
E-boxes
→ page 59

- 1 Solenoid valve
- 2 Solenoid valve

- 3 Solenoid valve
- 4 Supply plate

- 5 Blanking plate VABB-L1-10A


- 6 H-rail mounting
(two screws M4x25 to DIN 912 are required)

| Type | B1 | B2 | B3 | B4 | B5 | B6 | B7 | B8 | B9 | B10 | B11 | B12 |
|-----------------------|------|------|-------|-------|-------|-------|------|------|------|------|-------|-------|
| VUVG-B10A -...-F- ... | 84.9 | 62.4 | 39.12 | 34.95 | 29.83 | 17.75 | 8.15 | 24 | 7.15 | 43.5 | 45.75 | 39.15 |
| | B15 | D1 | D2 | D3 | D4 | D5 | H1 | H2 | H3 | H4 | H5 | H6 |
| | 0.48 | M7 | M5 | M5 | Ø 4.5 | Ø 4 | 53.1 | 12 | 9.1 | 6.3 | 11.57 | 3.6 |
| | H7 | H8 | H9 | H10 | H15 | L3 | L5 | L6 | L7 | L8 | L9 | L10 |
| | 13.1 | 4.2 | 16.2 | 6.8 | 1.9 | 7 | 12.5 | 10.5 | 10.2 | 10.5 | 16.5 | 14.7 |
| | L11 | L15 | | | | | | | | | | |
| | 14 | 8.5 | | | | | | | | | | |

| Valve positions | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 12 | 14 | 16 |
|-----------------|------|----|------|-----|------|-----|-------|-----|-------|-------|-------|-------|
| L1 [mm] | 42.5 | 53 | 63.5 | 74 | 84.5 | 96 | 106.5 | 116 | 126.5 | 147.5 | 168.5 | 189.5 |
| L2 [mm] | 28.5 | 39 | 49.5 | 60 | 70.5 | 81 | 91.5 | 102 | 112.5 | 133.5 | 154.5 | 175.5 |
| L4 [mm] | 35.5 | 46 | 56.5 | 67 | 77.5 | 89 | 99.5 | 109 | 119.5 | 140.5 | 161.5 | 182.5 |
| VABM weight [g] | 60 | 78 | 96 | 114 | 132 | 150 | 168 | 186 | 204 | 240 | 276 | 312 |

Solenoid valves VUVG-B10A, sub-base valves

Ordering data

| Technical data – Manifold rails ¹⁾ | | | | | | | | | |
|-----------------------------------------------------------------------------------|------------|---------|--------------|-----------------|-------------------------|-----------------------------|------------------------------------------|--------|------|
| | Connection | | | CRC | Material ³⁾ | Operating pressure [bar] | Max. tightening torque for assembly [Nm] | | |
| | 2, 4 | 1, 3, 5 | 12/14, 82/84 | | | | Valve | H-rail | Wall |
|  | M5 | M7 | M5 | 2 ²⁾ | Wrought aluminium alloy | -0.9 ... 10 | 0.45 | 1.5 | 1.5 |

- 1) Blanking plugs are included with the manifold rail.
- 2) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 3) Note on materials: RoHS-compliant

Order code – Manifold rails M3

| | | | | | | | | |
|---------------------------------------------|---|-------------|---|------------|---|---------------------------|---|----------|
| VABM | - | L1 | - | 10A | - | M7 | - | |
| Manifold assembly parts | | | | | | Number of valve positions | | |
| Manifold rail | | VABM | | | | 2 to 10, 12, 14 and 16 | | |
| Valve series | | | | | | Ports 1, 3, 5 | | |
| VUVG | | L1 | | | | M7 M7 | | |
| Valve width | | | | | | | | |
| 10 mm | | | | 10A | | | | |
| Rail with ports 1, 2, 3, 4, 5, 12/14, 82/84 | | | | | | | | |
| Port 2 and 4 in M5 | | | | | | | | W |

Ordering data – Accessories

| | | | Type |
|-------------------------------------------------------------------------------------|--------------------------|------------------------------|---------------------------------|
| Blanking plate | | | Technical data → Internet: vabb |
|  | For manifold rail 10AW | Incl. screws and seal | VABB-L1-10A |
| Separator | | | Technical data → Internet: vabd |
|  | For manifold rail 10AW | Separator for pressure zones | VABD-4.2-B |
| Supply plate | | | Technical data → Internet: vabf |
|  | For manifold rail 10AW | Incl. screws and seal | VABF-L1-10A-P3A4-M5 |
| Seals | | | Technical data → Internet: vabd |
|  | For sub-base valves B10A | 10 seals and 20 screws | VABD-L1-10AB-S-M3 |

Solenoid valves VUVG-B10, sub-base valves

FESTO

Technical data

Function

2x3/2C, 2x3/2U, 2x3/2H

5/2-way, single solenoid

5/2-way, double solenoid


5/3C, 5/3U, 5/3E

Circuit symbol → page 10

-  - Width 10 mm

-  - Flow rate
160 ... 270 l/min

-  - Voltage
5, 12 and 24 V DC



| General technical data | | | | | | | | | | | | |
|---------------------------------------|--------------------------------------------------|-----------------|-----------------|-------------------------------------|-----------------|-----------------|-------------------|----------|------------|-----------------|-----------------|-----------------|
| Valve function | T32-A | | | T32-M | | | M52-R | B52 | M52-M | P53 | | |
| Normal position | C ¹⁾ | U ²⁾ | H ⁴⁾ | C ¹⁾ | U ²⁾ | H ⁴⁾ | - | - | - | C ¹⁾ | U ²⁾ | E ³⁾ |
| Stable position | Monostable | | | | | | | Bistable | Monostable | Monostable | | |
| Pneumatic spring reset method | Yes | | | No | | | Yes ⁵⁾ | - | No | No | | |
| Mechanical spring reset method | No | | | Yes | | | Yes ⁵⁾ | - | Yes | Yes | | |
| Vacuum operation at port 1 | No | | | Only with external pilot air supply | | | | | | | | |
| Design | Piston spool valve | | | | | | | | | | | |
| Sealing principle | Soft | | | | | | | | | | | |
| Actuation type | Electric | | | | | | | | | | | |
| Type of control | Piloted | | | | | | | | | | | |
| Pilot air supply | External, internal; can be selected via sub-base | | | | | | | | | | | |
| Exhaust function | With flow control | | | | | | | | | | | |
| Manual override | Choice of non-detenting, detenting or covered | | | | | | | | | | | |
| Type of mounting | On manifold rail | | | | | | | | | | | |
| Mounting position | Any | | | | | | | | | | | |
| Nominal size [mm] | 2.7 | | | 1.8 | 1.7 | | 4 | | 2.3 | | 3.5 | |
| Standard nominal flow rate [l/min] | 170 | | | 150 | 140 | 140 | 330 | | 285 | | 300 | |
| Flow rate on manifold rail M5 [l/min] | 150 | | | 130 | 120 | 120 | 210 | | 180 | | 200 | |
| Flow rate on manifold rail M7 [l/min] | 160 | | | 140 | 130 | 130 | 270 | | 230 | | 250 | |
| Switching time on/off [ms] | 6/16 | | | 8/11 | | | 7/19 | | - | 8/24 | | 10/30 |
| Changeover time [ms] | - | | | - | | | - | | 7 | | 16 | |
| Width [mm] | 10 | | | | | | | | | | | |
| Connection | 1, 3, 5 | | | G1/8 in manifold rail | | | | | | | | |
| | 2, 4 | | | M5 or M7 in manifold rail | | | | | | | | |
| | 12/14, 82/84 | | | M5 in manifold rail | | | | | | | | |
| Product weight [g] | 55 | | | 54 | | | 45 | 55 | 44 | 55 | | |
| Corrosion resistance class | CRC | | | 2 ⁶⁾ | | | | | | | | |

1) C = Normally closed

2) U = Normally open

3) E = Normally exhausted

4) H=2x3/2-way valve in one housing with 1x normally closed and 1x normally open

5) Combined reset method

6) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Solenoid valves VUVG-B10, sub-base valves

Technical data

| Operating and environmental conditions | | | | | | |
|----------------------------------------|----------------|--------------------------------------------------------------------------------|---------------------|---------------------|-----------|---------------------------|
| Valve function | | T32-A ¹⁾ | T32-M ³⁾ | M52-R ²⁾ | B52 | M52-M ³⁾ P53 |
| Operating medium | | Filtered compressed air, grade of filtration 40 µm, lubricated or unlubricated | | | | |
| Operating pressure | Internal [bar] | 1.5 ... 8 | 3 ... 8 | 2.5 ... 8 | 1.5 ... 8 | 3 ... 8 |
| | External [bar] | 1.5 ... 10 | -0.9 ... 10 | | | -0.9 ... 8 -0.9 ... 10 |
| Pilot pressure ⁴⁾ [bar] | | 1.5 ... 8 | 2 ... 8 | 2.5 ... 8 | 1.5 ... 8 | 3 ... 8 |
| Ambient temperature [°C] | | -5 ... +50, -5 ... +60 with holding current reduction | | | | |
| Temperature of medium [°C] | | -5 ... +50, -5 ... +60 with holding current reduction | | | | |

- 1) Pneumatic spring
- 2) Mixed, pneumatic/mechanical spring
- 3) Mechanical spring
- 4) Minimum pilot pressure 50% of operating pressure

| Electrical data | |
|------------------------------|---------------------------------------------------|
| Electrical connection | Via E-box |
| Operating voltage [V DC] | 5, 12 and 24 ±10% |
| Power [W] | 1, reduced to 0.35 with holding current reduction |
| Duty cycle [%] | 100 |
| Protection class to EN 60529 | IP40 (with plug socket) |

| Information on materials | |
|--------------------------|-------------------------|
| Housing | Wrought aluminium alloy |
| Seals | HNBR, NBR |
| Note on materials | RoHS-compliant |

Dimensions

2x3/2-way, 5/2-way and 5/3-way valve

Download CAD data → www.festo.com

- - Note
More dimensions
E-boxes
→ page 59

1 Vertical electrical connection

2 Horizontal electrical connection










3 Manual override

| Type | B1 | H1 | H2 | L1 | L2 | L3 | L4 | L5 | L6 | L7 |
|---------------------|------|------|-----|------|------|----|------|------|------|------|
| VUVG-B10 -...-F ... | 10.2 | 32.5 | 3.6 | 86.5 | 81.5 | 8 | 4.85 | 6.15 | 69.2 | 66.7 |

Solenoid valves VUVG-B10, sub-base valves

Order code

FESTO

| | | | | | | |
|-------------------------------------------------------------------------------------|--------------------------|----|---|--|--|-------------|
| VUVG | - | 10 | - | | | |
| Valve design | | | | | | |
|  | | | | | | B |
| Sub-base, manifold valve incl. seal and screws | | | | | | |
| Width | | | | | | |
| 10 mm | | | | | | 10 |
| Valve functions | | | | | | |
|  | | | | | | T32C |
|  | | | | | | T32U |
|  | | | | | | T32H |
|  | | | | | | M52 |
|  | | | | | | B52 |
|  | | | | | | P53C |
|  | | | | | | P53U |
|  | | | | | | P53E |
| Reset method | | | | | | |
| Pneumatic spring for T32 and M52 | | | | | | A |
| Mechanical spring for T32 and M52 | | | | | | M |
| Pneu./mech. spring for M52 | | | | | | R |
| With B52 and P53 | | | | | | - |
| Pilot air supply | | | | | | |
| External | | | | | | Z |
| Manual override | | | | | | |
|  | Non-detenting | | | | | H |
|  | Covered | | | | | S |
| - | Non-detenting, detenting | | | | | T |

| | | | | | | | | |
|-----------------------------|----------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------|--|--|----------|---|--|
| | | | | | | L | - | |
| Connecting cables | | | | | | | | |
| W1...4 | Not sheathed |  | | | | | | |
| C1...4 | Sheathed | | for H | | | | | |
| WS1...4 | Not sheathed |  | | | | | | |
| S1...4 | Sheathed | | for S | | | | | |
| N1...4 | M8x1, 4-pin |  | | | | | | |
| N5...8 | M8x1, 4-pin |  | | | | | | |
| Display | | | | | | | | |
| L | LED | | | | | | | |
| Protective circuit | | | | | | | | |
| - | Without holding current reduction (HCR) | | | | | | | |
| R | With holding current reduction (HCR) | | | | | | | |
| E-box | | | | | | | | |
| H2 | Connection pattern H, horizontal plug | |  | | | | | |
| H3 | Connection pattern H, vertical plug | |  | | | | | |
| S2 | Connection pattern S, horizontal plug | |  | | | | | |
| S3 | Connection pattern S, vertical plug | |  | | | | | |
| L1...4 | With 2x flying leads L: 1 = 0.5 m, 2 = 1 m, 3 = 2.5 m, 4 = 5 m | |  | | | | | |
| K6...9 | Cable: K6 = 0.5 m, K7 = 1 m, K8 = 2.5 m, K9 = 5 m | |  | | | | | |
| R1 | Individual plug M8, 4-pin | |  | | | | | |
| R8 | Individual plug M8, 3-pin | |  | | | | | |
| P3 | Without E-box | |  | | | | | |
| Operating voltage | | | | | | | | |
| 1 | 24 V DC | | | | | | | |
| 5 | 12 V DC | | | | | | | |
| 4 | 5 V DC | | | | | | | |
| Pneumatic connection | | | | | | | | |
| F | In the manifold rail | | | | | | | |

Solenoid valves VUVG-B10, sub-base valves


Manifold assembly

Sub-base valve for manifold assembly
M5 or M7 connection



Dimensions

Download CAD data → www.festo.com




| Type | B1 | B2 | B3 | B4 | B5 | B6 | B7 | B8 | B9 | B10 | B11 | B12 |
|----------------------|------|-------|------|------|-------|------|-----|-----|------|------|-------|------|
| VUVG-B10 -...-F- ... | 97.5 | 74.8 | 52.9 | 46.5 | 40.9 | 24.9 | 8.9 | 62 | 57.7 | 16.9 | 16 | 42.2 |
| | B13 | B14 | B15 | D1 | D2 | D3 | D4 | D5 | H1 | H2 | H3 | H4 |
| | 39.3 | 14.05 | 1.2 | G1/8 | M5/M7 | M5 | 4.5 | ∅ 6 | 56.4 | 15.7 | 12.17 | 7.87 |
| | H5 | H6 | H7 | H8 | H9 | H10 | H11 | L3 | L4 | L5 | L6 | L7 |
| | 23.9 | 10.8 | 4 | 17.6 | 5.9 | 18 | 6.8 | 4 | 10.5 | 10.2 | 16 | 11 |
| | L8 | L9 | L15 | | | | | | | | | |
| | 1 | 3 | 10 | | | | | | | | | |

| Valve positions | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 12 | 14 | 16 | 22 |
|-----------------|------|-----|------|-----|------|-----|-------|-----|-------|-------|-------|-------|-------|
| L1 [mm] | 48.5 | 59 | 69.5 | 80 | 90.5 | 101 | 111.5 | 122 | 132.5 | 153.5 | 174.5 | 195.5 | 258.5 |
| L2 [mm] | 30.5 | 41 | 51.5 | 62 | 72.5 | 83 | 93.5 | 104 | 114.5 | 135.5 | 156.5 | 177.5 | 240.5 |
| VABM weight [g] | 107 | 135 | 163 | 191 | 219 | 247 | 275 | 303 | 331 | 387 | 415 | 471 | 499 |

Solenoid valves VUVG-B10, sub-base valves

Ordering data

| Technical data – Manifold rails ¹⁾ | | | | | | | | | |
|-----------------------------------------------------------------------------------|------------|---------|--------------|-----------------|-------------------------|-----------------------------|------------------------------------------|--------|------|
| | Connection | | | CRC | Material ³⁾ | Operating pressure [bar] | Max. tightening torque for assembly [Nm] | | |
| | 2, 4 | 1, 3, 5 | 12/14, 82/84 | | | | Valve | H-rail | Wall |
|  | M5 or M7 | G1/8 | M5 | 2 ²⁾ | Wrought aluminium alloy | -0.9 ... 10 | 0.45 | 1.5 | 3 |

- 1) Blanking plugs are included with the manifold rail.
- 2) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 3) Note on materials: RoHS-compliant

Order code – Manifold rails M5 and M7

| | | | | | | | | |
|------------------------------------------------------|-------------|-----------|---|-----------|------------|---------------------------|------------------------|-----------|
| VABM | - | L1 | - | 10 | - | G18 | - | |
| Manifold assembly parts | | | | | | Number of valve positions | | |
| Manifold rail | VABM | | | | | | 2 to 10, 12, 14 and 16 | |
| Valve series | | | | | | Ports 1, 3, 5 | | |
| VUVG | L1 | | | | G18 | | G1/8 | |
| Valve width | | | | | | | | |
| 10 mm | | | | 10 | | | | |
| Manifold rail with ports 1, 2, 3, 4, 5, 12/14, 82/84 | | | | | | | | |
| Port 2 and 4 in M5 | | | | | | | | W |
| Port 2 and 4 in M7 | | | | | | | | HW |

Ordering data – Accessories

| | | | Type |
|-------------------------------------------------------------------------------------|-------------------------------------------------|------------------------------|---------------------------|
| Blanking plate Technical data → Internet: vabb | | | |
|  | For manifold rail 10W/10HW, sub-base valves | Incl. screws and seal | VABB-L1-10-W |
| Separator Technical data → Internet: vabd | | | |
|  | For manifold rail 10W and 10HW, sub-base valves | Separator for pressure zones | VABD-6-B |
| Supply plate Technical data → Internet: vabf | | | |
|  | For manifold rail 10W | Incl. screws and seal | VABF-L1-10-P3A4-M5 |
| | For manifold rail 10HW | | VABF-L1-10-P3A4-M7 |
| Seals Technical data → Internet: vabd | | | |
|  | For sub-base valves B10 | 10 seals and 20 screws | VABD-L1-10B-S-M7 |

Solenoid valves VUVG-B14, sub-base valves

Technical data

Function

2x3/2C, 2x3/2U, 2x3/2H
 5/2-way, single solenoid
 5/2-way, double solenoid
 5/3C, 5/3U, 5/3E

 - Width 14 mm

 - Flow rate
 510 ... 700 l/min

 - Voltage
 5, 12 and 24 V DC

Circuit symbol → page 10

| General technical data | | | | | | | | | | | | |
|------------------------------------------------------------------|--------------------------------------------------|-----------------|-----------------|------------------------------------------------|-----------------|-----------------|-------|----------|------------|-----------------|-----------------|-----------------|
| Valve function | T32-A | | | T32-M | | | M52-A | B52 | M52-M | P53 | | |
| Normal position | C ¹⁾ | U ²⁾ | H ⁴⁾ | C ¹⁾ | U ²⁾ | H ⁴⁾ | - | - | - | C ¹⁾ | U ²⁾ | E ³⁾ |
| Stable position | Monostable | | | | | | | Bistable | Monostable | Monostable | | |
| Pneumatic spring reset method | Yes | | | No | | | Yes | - | No | No | | |
| Mechanical spring reset method | No | | | Yes | | | No | - | Yes | Yes | | |
| Vacuum operation at port 1 | No | | | Only with external pilot air supply | | | | | | | | |
| Design | Piston spool valve | | | | | | | | | | | |
| Sealing principle | Soft | | | | | | | | | | | |
| Actuation type | Electric | | | | | | | | | | | |
| Type of control | Piloted | | | | | | | | | | | |
| Pilot air supply | External, internal; can be selected via sub-base | | | | | | | | | | | |
| Exhaust function | With flow control | | | | | | | | | | | |
| Manual override | Choice of non-detenting, detenting or covered | | | | | | | | | | | |
| Type of mounting | On manifold rail | | | | | | | | | | | |
| Mounting position | Any | | | | | | | | | | | |
| Nominal size [mm] | 4.6 | | | 4.3 | | | 5.4 | | | | | |
| Standard nominal flow rate [l/min] | 600 | 580 | | 470 | 450 | 450 | 680 | | | 600 | 580 | 580 |
| Flow rate on manifold rail G ¹ / ₈ [l/min] | 540 | 510 | 540 | 430 | 410 | 410 | 580 | | | 540 | 510 | 510 |
| Switching time on/off [ms] | 8/23 | | | 11/15 | | | 14/28 | - | 13/40 | 12/40 | | |
| Changeover time [ms] | - | | | | | | | 8 | | | 20 | |
| Width [mm] | 14 | | | | | | | | | | | |
| Port | 1, 3, 5 | | | G ¹ / ₄ in manifold rail | | | | | | | | |
| | 2, 4 | | | G ¹ / ₈ in manifold rail | | | | | | | | |
| | 12/14, 82/84 | | | M5 in manifold rail | | | | | | | | |
| Product weight [g] | 89 | | | 80 | | | 78 | 89 | 70 | 89 | | |
| Corrosion resistance class | CRC | | | 2 ⁶⁾ | | | | | | | | |

1) C = Normally closed

2) U = Normally open

3) E = Normally exhausted

4) H=2x3/2-way valve in one housing with 1x normally closed and 1x normally open

6) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Solenoid valves VUVG-B14, sub-base valves

FESTO

Technical data

| Operating and environmental conditions | | T32-A ¹⁾ | T32-M ³⁾ | M52-A ¹⁾ | B52 | M52-M ³⁾ | P53 |
|----------------------------------------|----------------|--------------------------------------------------------------------------------|---------------------|---------------------|-----------|---------------------|-------------|
| Valve function | | Filtered compressed air, grade of filtration 40 µm, lubricated or unlubricated | | | | | |
| Operating pressure | Internal [bar] | 1.5 ... 8 | 3 ... 8 | 2.5 ... 8 | 1.5 ... 8 | 3 ... 8 | |
| | External [bar] | 1.5 ... 10 | -0.9 ... 10 | | | -0.9 ... 8 | -0.9 ... 10 |
| Pilot pressure ⁴⁾ [bar] | | 1.5 ... 8 | 2 ... 8 | 2.5 ... 8 | 1.5 ... 8 | 3 ... 8 | |
| Ambient temperature [°C] | | -5 ... +50, -5 ... +60 with holding current reduction | | | | | |
| Temperature of medium [°C] | | -5 ... +50, -5 ... +60 with holding current reduction | | | | | |

- 1) Pneumatic spring
- 3) Mechanical spring
- 4) Minimum pilot pressure 50% of operating pressure

| Electrical data | |
|------------------------------|---------------------------------------------------|
| Electrical connection | Via E-box |
| Operating voltage [V DC] | 5, 12 and 24 ±10% |
| Power [W] | 1, reduced to 0.35 with holding current reduction |
| Duty cycle [%] | 100 |
| Protection class to EN 60529 | IP40 (with plug socket) |

| Information on materials | |
|--------------------------|-------------------------|
| Housing | Wrought aluminium alloy |
| Seals | HNBR, NBR |
| Note on materials | RoHS-compliant |

Dimensions Download CAD data → www.festo.com

2x3/2-way, 5/2-way and 5/3-way valve










1 Horizontal electrical connection 2 Manual override

Note
More dimensions
E-boxes
→ page 59

| Type | B1 | H1 | L1 | L2 | L3 | L4 | L5 | L6 | L7 | L8 |
|--------------------|------|------|-----|-----|----|------|------|------|-------|-------|
| VUVG-B14 ...-F ... | 14.4 | 34.8 | 107 | 102 | 8 | 66.5 | 4.85 | 6.15 | 89.45 | 86.95 |

Solenoid valves VUVG-B14, sub-base valves

Order code

| | | | | | | |
|---------------------------------------------------------------------------------------------------------------------------------------------|---|----|---|--|--|-------------|
| VUVG | - | 14 | - | | | |
| Valve design | | | | | | |
|  <p>Sub-base, manifold valve incl. seal and screws</p> | | | | | | B |
| Width | | | | | | |
| 14 mm | | | | | | 14 |
| Valve functions | | | | | | |
|  | | | | | | T32C |
|  | | | | | | T32U |
|  | | | | | | T32H |
|  | | | | | | M52 |
|  | | | | | | B52 |
|  | | | | | | P53C |
|  | | | | | | P53U |
|  | | | | | | P53E |
| Reset method | | | | | | |
| Pneumatic spring for T32 and M52 | | | | | | A |
| Mechanical spring for T32 and M52 | | | | | | M |
| With B52 and P53 | | | | | | - |
| Pilot air supply | | | | | | |
| External | | | | | | Z |
| Manual override | | | | | | |
|  Non-detenting | | | | | | H |
|  Covered | | | | | | S |
| - Non-detenting, detenting | | | | | | T |


| | | | | | |
|-----------------------------------------------|----------------------------------------------------------------|---------------------------------------------------------------------------------------|--|----------|---|
| | | | | L | - |
| Connecting cables | | | | | |
| W1...4 | Not sheathed |  | | | |
| C1...4 | Sheathed | for H | | | |
| WS1...4 | Not sheathed |  | | | |
| S1...4 | Sheathed | for S | | | |
| N1...4 | M8x1, 4-pin |  | | | |
| N5...8 | M8x1, 4-pin |  | | | |
| Display | | | | | |
| L | LED | | | | |
| Protective circuit | | | | | |
| - Without holding current reduction (HCR) | | | | | |
| R With holding current reduction (HCR) | | | | | |
| E-box | | | | | |
| H2 | Connection pattern H, horizontal plug |  | | | |
| H3 | Connection pattern H, vertical plug |  | | | |
| S2 | Connection pattern S, horizontal plug |  | | | |
| S3 | Connection pattern S, vertical plug |  | | | |
| L1...4 | With 2x flying leads L: 1 = 0.5 m, 2 = 1 m, 3 = 2.5 m, 4 = 5 m |  | | | |
| K6...9 | Cable: K6 = 0.5 m, K7 = 1 m, K8 = 2.5 m, K9 = 5 m |  | | | |
| R1 | Individual plug M8, 4-pin |  | | | |
| R8 | Individual plug M8, 3-pin |  | | | |
| P3 | Without E-box |  | | | |
| Operating voltage | | | | | |
| 1 | 24 V DC | | | | |
| 5 | 12 V DC | | | | |
| 4 | 5 V DC | | | | |
| Pneumatic connection | | | | | |
| F | In the manifold rail | | | | |

Solenoid valves VUVG-B14, sub-base valves

Manifold assembly




Sub-base valve for manifold assembly
G $\frac{1}{8}$ connection



Dimensions

Download CAD data → www.festo.com



Note
More dimensions
E-boxes
→ page 59

1 Blanking plate VABB-L1-14
2 Supply plate
VABF-L1-14-P3A4-G18

3 Double solenoid valve

4 Single solenoid valve


5 H-rail mounting
(two M4x25 screws to DIN 912 are required)

| Type | B1 | B2 | B3 | B4 | B5 | B6 | B7 | B8 | B9 | B10 | B11 | B12 |
|----------------------|-------|------|-----------------|-----------------|------|-------|-------|------|------|------|------|------|
| VUVG-B14 -...-F- ... | 118.3 | 95.1 | 67.7 | 58.2 | 56.3 | 36.6 | 16.7 | 4.5 | 72.9 | 26.5 | 20 | 49.1 |
| | B13 | B15 | D1 | D2 | D3 | D4 | D5 | H1 | H2 | H3 | H4 | H5 |
| | 49.1 | 1.2 | G $\frac{1}{4}$ | G $\frac{1}{8}$ | M5 | Ø 4.5 | Ø 9.8 | 64.3 | 19.6 | 15.3 | 10.1 | 29.5 |
| | H6 | H7 | H8 | H9 | H10 | H11 | H12 | L3 | L5 | L6 | L7 | L8 |
| | 9.83 | 4.8 | 22.1 | 7 | 15.4 | 6.8 | 23.9 | 6 | 1 | 16 | 14.4 | 11.3 |
| | L9 | L10 | L11 | | | | | | | | | |
| | 18.5 | 16 | 14 | | | | | | | | | |

Solenoid valves VUVG-B14, sub-base valves

Ordering data

| Valve positions | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 12 | 14 | 16 |
|-----------------|------|------|------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| L1 [mm] | 56.3 | 72.3 | 88.3 | 104.3 | 120.3 | 136.3 | 152.3 | 168.3 | 184.3 | 216.3 | 248.3 | 280.3 |
| L2 [mm] | 40 | 56 | 72 | 88 | 104 | 120 | 136 | 152 | 168 | 200 | 232 | 264 |
| L4 [mm] | 54.3 | 70.3 | 86.3 | 102.3 | 118.3 | 134.3 | 150.3 | 166.3 | 182.3 | 214.3 | 246.6 | 278.3 |
| VABM weight [g] | 232 | 306 | 380 | 454 | 528 | 602 | 676 | 750 | 824 | 972 | 1,120 | 1,268 |



| Technical data – Manifold rails ¹⁾ | | | | | | | | | |
|-----------------------------------------------------------------------------------|-------------------------------|-------------------------------|-----------------|-----------------|-------------------------|-----------------------------|------------------------------------------|--------|------|
| | Connection | | | CRC | Material ³⁾ | Operating pressure [bar] | Max. tightening torque for assembly [Nm] | | |
| | 2, 4 | 1, 3, 5 | 12/14, 82/84 | | | | Valve | H-rail | Wall |
|  | G ¹ / ₈ | G ¹ / ₄ | M5 | 2 ²⁾ | Wrought aluminium alloy | -0.9 ... 10 | 0.65 | 1.5 | 3 |

- 1) Blanking plugs are included with the manifold rail.
- 2) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 3) Note on materials: RoHS-compliant

Order code – Manifold rails G¹/₈

| | | | | | | | | | |
|------------------------------------------------------|---|-------------|---|-----------|-----------|---|------------|-----------------------------------|---------------------------|
| VABM | - | L1 | - | 14 | W | - | G14 | - | |
| Manifold assembly parts | | | | | | | | | Number of valve positions |
| Manifold rail | | VABM | | | | | | | 2 to 10, 12, 14 and 16 |
| Valve series | | | | | | | | | Ports 1, 3, 5 |
| VUVG | | L1 | | | | | G14 | G¹/₄ | |
| Valve width | | | | | | | | | |
| 14 mm | | | | | 14 | | | | |
| Manifold rail with ports 1, 2, 3, 4, 5, 12/14, 82/84 | | | | | | | | | |
| Port 2 and 4 in G ¹ / ₈ | | | | | W | | | | |

Ordering data – Accessories

| | | | Type |
|-------------------------------------------------------------------------------------|----------------------------------------|------------------------------|----------------------------|
| Blanking plate Technical data → Internet: vabb | | | |
|  | For manifold rail 14W, sub-base valves | Incl. screws and seal | VABB-L1-14 |
| Separator Technical data → Internet: vabd | | | |
|  | For manifold rail 14W, sub-base valves | Separator for pressure zones | VABD-10-B |
| Supply plate Technical data → Internet: vabf | | | |
|  | For manifold rail 14W | Incl. screws and seal | VABF-L1-14-P3A4-G18 |
| Seals Technical data → Internet: vabd | | | |
|  | For sub-base valves B14 | 10 seals and 20 screws | VABD-L1-14B-S-G18 |

Solenoid valves VUVG-B18, sub-base valves

Technical data

Function

2x3/2C, 2x3/2U, 2x3/2H
 5/2-way, single solenoid
 5/2-way, double solenoid
 5/3C, 5/3U, 5/3E

Circuit symbol → page 10

-  - Width 18 mm
-  - Flow rate
900 ... 1,000 l/min
-  - Voltage
5, 12 and 24 V DC



| General technical data | | | | | | | | | | | | |
|------------------------------------|--------------------------------------------------|-----------------|-----------------|------------------------------------------------|-----------------|-----------------|-------------------|----------|------------|-----------------|-----------------|-----------------|
| Valve function | T32-A | | | T32-M | | | M52-R | B52 | M52-M | P53 | | |
| Normal position | C ¹⁾ | U ²⁾ | H ⁴⁾ | C ¹⁾ | U ²⁾ | H ⁴⁾ | – | – | – | C ¹⁾ | U ²⁾ | E ³⁾ |
| Stable position | Monostable | | | | | | | Bistable | Monostable | Monostable | | |
| Pneumatic spring reset method | Yes | | | No | | | Yes ⁵⁾ | – | No | No | | |
| Mechanical spring reset method | No | | | Yes | | | Yes ⁵⁾ | – | Yes | Yes | | |
| Vacuum operation at port 1 | No | | | Only with external pilot air supply | | | | | | | | |
| Design | Piston spool valve | | | | | | | | | | | |
| Sealing principle | Soft | | | | | | | | | | | |
| Actuation type | Electric | | | | | | | | | | | |
| Type of control | Piloted | | | | | | | | | | | |
| Pilot air supply | External, internal; can be selected via sub-base | | | | | | | | | | | |
| Exhaust function | With flow control | | | | | | | | | | | |
| Manual override | Choice of non-detenting, detenting or covered | | | | | | | | | | | |
| Type of mounting | On manifold rail | | | | | | | | | | | |
| Mounting position | Any | | | | | | | | | | | |
| Nominal size [mm] | 5.7 | | | | | | 6.9 | 7.3 | 6.9 | 6.5 | | |
| Standard nominal flow rate [l/min] | 900 | | | | | | 1,150 | | | 1,080 | | |
| Flow rate on manifold rail | 800 | | | | | | 1,000 | | | 950 | | |
| Switching time on/off [ms] | 13/27 | | | 15/22 | | | 15/31 | – | 10/45 | 15/48 | | |
| Changeover time [ms] | – | | | | | | 11 | | 29 | | | |
| Width [mm] | 18 | | | | | | | | | | | |
| Port | 1, 3, 5 | | | G ³ / ₈ in manifold rail | | | | | | | | |
| | 2, 4 | | | G ¹ / ₄ in manifold rail | | | | | | | | |
| | 12/14, 82/84 | | | M5 in manifold rail | | | | | | | | |
| Product weight [g] | 164 | | | | | | 154 | 160 | 154 | 160 | | |
| Corrosion resistance class | CRC | | | 2 ⁶⁾ | | | | | | | | |

1) C = Normally closed
 2) U = Normally open
 3) E = Normally exhausted
 4) H=2x3/2-way valve in one housing with 1x normally closed and 1x normally open
 5) Combined reset method
 6) Corrosion resistance class 2 according to Festo standard 940 070
 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Solenoid valves VUVG-B18, sub-base valves

Technical data

| Operating and environmental conditions | | | | | | | | |
|----------------------------------------|--------------------------------------------------------------------------------|-------|-------------------------------------------------------|---------------------|---------------------|-----------|---------------------|-------------|
| Valve function | | | T32-A ¹⁾ | T32-M ³⁾ | M52-R ²⁾ | B52 | M52-M ³⁾ | P53 |
| Operating medium | Filtered compressed air, grade of filtration 40 µm, lubricated or unlubricated | | | | | | | |
| Operating pressure | Internal | [bar] | 1,5 ... 8 | 3,5 ... 8 | 2,5 ... 8 | 1,5 ... 8 | 3 ... 8 | |
| | External | [bar] | 1,5 ... 10 | -0,9 ... 10 | | | -0,9 ... 8 | -0,9 ... 10 |
| Pilot pressure ⁴⁾ | | [bar] | 1,5 ... 8 | 3 ... 8 | 2,5 ... 8 | 1,5 ... 8 | 3 ... 8 | |
| Ambient temperature | | [°C] | -5 ... +50, -5 ... +60 with holding current reduction | | | | | |
| Temperature of medium | | [°C] | -5 ... +50, -5 ... +60 with holding current reduction | | | | | |


- 1) Pneumatic spring
- 2) Mixed, pneumatic/mechanical spring
- 3) Mechanical spring
- 4) Minimum pilot pressure 50% of operating pressure

| Electrical data | |
|------------------------------|-------------------------------------------------------|
| Electrical connection | Via E-box |
| Operating voltage | [V DC] 5, 12 and 24 ±10% |
| Power | [W] 1, reduced to 0.35 with holding current reduction |
| Duty cycle | [%] 100 |
| Protection class to EN 60529 | IP40 (with plug socket) |

| Information on materials | |
|--------------------------|-------------------------|
| Housing | Wrought aluminium alloy |
| Seals | HNBR, NBR |
| Note on materials | RoHS-compliant |

Dimensions

2x3/2-way, 5/2-way and 5/3-way valve



1 Horizontal electrical connection 2 Manual override

Download CAD data → www.festo.com










 Note

More dimensions
E-boxes
→ page 59

| Type | B1 | H1 | L1 | L2 | L3 | L4 | L5 |
|---------------------|------|------|-------|-------|------|-------|-------|
| VUVG-B18 -...-F ... | 18.3 | 43.1 | 129.4 | 124.4 | 86.4 | 112.2 | 109.7 |

Solenoid valves VUVG-B18, sub-base valves

Order code


| | | | | | | |
|-------------------------------------------------------------------------------------|--------------------------|-----------|---|--|--|-------------|
| VUVG | - | 18 | - | | | |
| Valve design | | | | | | |
|  | | B | | | | |
| Sub-base, manifold valve incl. seal and screws | | | | | | |
| Width | | | | | | |
| 18 mm | | | | | | 18 |
| Valve functions | | | | | | |
|  | | | | | | T32C |
| 12/14 82/84 1 5 3 | 4 | 2 | | | | |
|  | | | | | | T32U |
| 10(14) 82/84 1 5 3 | 4 | 2 | | | | |
|  | | | | | | T32H |
| 14/10 82/84 1 5 3 | 4 | 2 | | | | |
|  | | | | | | M52 |
| 14 84 5 1 3 | 4 | 2 | | | | |
|  | | | | | | B52 |
| 14 84 5 1 3 | 4 | 2 | | | | |
|  | | | | | | P53C |
| 14 84 5 1 3 | 4 | 2 | | | | |
|  | | | | | | P53U |
| 14 84 5 1 3 | 4 | 2 | | | | |
|  | | | | | | P53E |
| 14 84 5 1 3 | 4 | 2 | | | | |
| Reset method | | | | | | |
| Pneumatic spring for T32 and M52 | | | | | | A |
| Mechanical spring for T32 and M52 | | | | | | M |
| | | | | | | R |
| With B52 and P53 | | | | | | - |
| Pilot air supply | | | | | | |
| External | | | | | | Z |
| Manual override | | | | | | |
|  | Non-detenting | | | | | H |
|  | Covered | | | | | S |
| - | Non-detenting, detenting | | | | | T |

| | | | | | | | | |
|-----------------------------|----------------------------------------------------------------|--|--|--|---------------------------------------------------------------------------------------|----------|---|--|
| | | | | | | L | - | |
| Connecting cables | | | | | | | | |
| W1...4 | Not sheathed | | | |  | | | |
| C1...4 | Sheathed | | | | for H | | | |
| WS1...4 | Not sheathed | | | |  | | | |
| S1...4 | Sheathed | | | | for S | | | |
| N1...4 | M8x1, 4-pin | | | |  | | | |
| N5...8 | M8x1, 4-pin | | | |  | | | |
| Display | | | | | | | | |
| L | LED | | | | | | | |
| Protective circuit | | | | | | | | |
| - | Without holding current reduction (HCR) | | | | | | | |
| R | With holding current reduction (HCR) | | | | | | | |
| E-box | | | | | | | | |
| H2 | Connection pattern H, horizontal plug | | | |  | | | |
| H3 | Connection pattern H, vertical plug | | | |  | | | |
| S2 | Connection pattern S, horizontal plug | | | |  | | | |
| S3 | Connection pattern S, vertical plug | | | |  | | | |
| L1...4 | With 2x flying leads L: 1 = 0.5 m, 2 = 1 m, 3 = 2.5 m, 4 = 5 m | | | |  | | | |
| K6...9 | Cable: K6 = 0.5 m, K7 = 1 m, K8 = 2.5 m, K9 = 5 m | | | |  | | | |
| R1 | Individual plug M8, 4-pin | | | |  | | | |
| R8 | Individual plug M8, 3-pin | | | |  | | | |
| P3 | Without E-box | | | |  | | | |
| Operating voltage | | | | | | | | |
| 1 | 24 V DC | | | | | | | |
| 5 | 12 V DC | | | | | | | |
| 4 | 5 V DC | | | | | | | |
| Pneumatic connection | | | | | | | | |
| F | In the manifold rail | | | | | | | |

Solenoid valves VUVG-B18, sub-base valves


Manifold assembly

Sub-base valve for manifold assembly
G $\frac{1}{4}$ connection



Dimensions

Download CAD data → www.festo.com



Note
More dimensions
E-boxes
→ page 59


- 1 Ports 1, 3 and 5: G $\frac{3}{8}$ (at both ends)
- 2 Ports 2 and 4: G $\frac{1}{4}$
- 3 Port 12/14 for external pilot air: M5
- 4 Port 82/84 for external pilot air: M5
- 5 Supply plate, ports 1, 3 and 5: G $\frac{1}{4}$
VABF-L1-14-P3A4-G18
- 6 Blanking plate
- 7 Double solenoid valve
- 8 Single solenoid valve
- 9 H-rail mounting (two M4x40 screws to DIN 912 are required)

| Type | B1 | B2 | B3 | B4 | B5 | B6 | B7 | B8 | B9 | B10 | B11 | D1 |
|----------------------|-------|--------|------|------|------|------|------|------|-----|------|------|-----|
| VUVG-B18 -...-F- ... | 129.4 | 124.41 | 95.6 | 73.1 | 47.8 | 22.5 | 51.7 | 34.8 | 26 | 90.6 | 76.8 | 4.5 |
| | H1 | H2 | H3 | H4 | H5 | H6 | H7 | H8 | H9 | H10 | H11 | H12 |
| | 81.6 | 38.5 | 11.5 | 28.4 | 27.6 | 19 | 12 | 12.1 | 6.1 | 29.1 | 8.8 | 6.5 |
| | L3 | L4 | L5 | L6 | L7 | L8 | L9 | L10 | | | | |
| | 6 | 23 | 19 | 20.8 | 19 | 15.6 | 8.5 | 1 | | | | |

Solenoid valves VUVG-B18, sub-base valves

Ordering data

| Valve positions | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 12 | 14 | 16 |
|-----------------|------|------|-------|-------|-------|-------|-------|-------|-------|-------|-------|-------|
| L1 [mm] | 63.5 | 82.5 | 101.5 | 120.5 | 139.5 | 158.5 | 177.5 | 196.5 | 215.5 | 253.5 | 291.5 | 329.5 |
| L2 [mm] | 49 | 68 | 87 | 106 | 125 | 144 | 163 | 182 | 201 | 239 | 277 | 315 |
| VABM weight [g] | 232 | 306 | 380 | 454 | 528 | 602 | 676 | 750 | 824 | 972 | 1,120 | 1,268 |


| Technical data – Manifold rails ¹⁾ | | | | | | | | | |
|-----------------------------------------------------------------------------------|-----------------|-----------------|--------------|-----------------|-------------------------|--------------------------|------------------------------------------|--------|------|
| | Connection | | | CRC | Material ³⁾ | Operating pressure [bar] | Max. tightening torque for assembly [Nm] | | |
| | 2, 4 | 1, 3, 5 | 12/14, 82/84 | | | | Valve | H-rail | Wall |
|  | G $\frac{1}{4}$ | G $\frac{3}{8}$ | M5 | 2 ²⁾ | Wrought aluminium alloy | -0.9 ... 10 | | | |

- 1) Blanking plugs are included with the manifold rail.
- 2) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 3) Note on materials: RoHS-compliant

Order code – Manifold rails G $\frac{1}{4}$

| | | | | | | | | | |
|------------------------------------------------------|---|-------------|---|-----------|-----------|---|------------|---|---------------------------|
| VABM | - | L1 | - | 18 | W | - | G38 | - | |
| Manifold assembly parts | | | | | | | | | Number of valve positions |
| Manifold rail | | VABM | | | | | | | 2 to 10, 12, 14 and 16 |
| Valve series | | | | | | | | | Ports 1, 3, 5 |
| VUVG | | L1 | | | | | G38 | | G $\frac{3}{8}$ |
| Valve width | | | | | | | | | |
| 18 mm | | | | | 18 | | | | |
| Manifold rail with ports 1, 2, 3, 4, 5, 12/14, 82/84 | | | | | | | | | |
| Port 2 and 4 in G $\frac{1}{4}$ | | | | | W | | | | |

Ordering data – Accessories


| | | | | Type |
|-------------------------------------------------------------------------------------|----------------------------------------|------------------------------|--|---------------------------------|
| Blanking plate | | | | Technical data → Internet: vabb |
|  | For manifold rail 18W, sub-base valves | Incl. screws and seal | | VABB-L1-18 |
| Separator | | | | Technical data → Internet: vabd |
|  | For manifold rail 18W, sub-base valves | Separator for pressure zones | | VABD-14-B |
| Supply plate | | | | Technical data → Internet: vabf |
|  | For manifold rail 18W | Incl. screws and seal | | VABF-L1-18-P3A4-G14 |
| Seals | | | | Technical data → Internet: vabd |
|  | For sub-base valves B18 | 10 seals and 20 screws | | VABD-L1-18B-S-G14 |

Solenoid valves VUVG

E-boxes


Protective circuit without holding current reduction

The solenoid coils (P type) of the 5, 12 and 24 V designs are equipped with a protective circuit to arrest sparks and protect against polarity reversal.



Protective circuit with holding current reduction

The 24 V DC design (R type) additionally features holding current reduction. This reduces the power from 1 W to 0.35 W.



| Pin allocation for E-box | | | |
|------------------------------------------------------------|---------------------------------|--------|-----------------------------------|
| | Pin | | |
| Rectangular plug, pin spacing 4 mm, connection pattern H | | | |
| | VAVE-L1-1VH2-LP/VAVE-L1-1VH3-LP | | |
| | 1 | + or - | Without holding current reduction |
| | 2 | + or - | |
| | VAVE-L1-1H2-LR/VAVE-L1-1H3-LR | | With holding current reduction |
| 1 | - | | |
| 2 | + | | |
| Rectangular plug, pin spacing 2.5 mm, connection pattern S | | | |
| | VAVE-L1-1VS2-LP/VAVE-L1-1VS3-LP | | |
| | 1 | + or - | Without holding current reduction |
| | 2 | + or - | |
| | VAVE-L1-1S2-LR/VAVE-L1-1S3-LR | | With holding current reduction |
| 1 | - | | |
| 2 | + | | |
| Flying leads, 2-pin | | | |
| | VAVE-L1-1VL1...4-LP | | |
| | 1 | + or - | Without holding current reduction |
| | 2 | + or - | |
| | VAVE-L1-1L1...4-LR | | With holding current reduction |
| 1 | - | | |
| 2 | + | | |

Solenoid valves VUVG

E-boxes



| Pin allocation for E-box | | | |
|--------------------------|-----------------|----------|-----------------------------------|
| | Pin | | |
| Round plug, M8, 3-pin | | | |
| | VAVE-L1-1VR8-LP | | |
| | 1 | Not used | Without holding current reduction |
| | 3 | + or - | |
| | 4 | + or - | |
| Round plug, M8, 4-pin | | | |
| | VAVE-L1-1VR1-LP | | |
| | 1 | Not used | Without holding current reduction |
| | 2 | Not used | |
| | 3 | + or - | |
| | 4 | + or - | |

Solenoid valves VUVG

E-boxes

| General technical data | | | | | | | |
|----------------------------------|----------------|----|----|----|--------------|---------------------------|---------------------------|
| Variants | H2 | H3 | S2 | S3 | L- | R1 | R8 |
| Mounting position | Any | | | | | | |
| Electrical connection | 2-pin, socket | | | | Flying leads | Individual plug M8, 4-pin | Individual plug M8, 3-pin |
| Protection class | IP40 | | | | | IP65 | |
| Switching position display | LED | | | | | | |
| Type of mounting | Clip | | | | | Self-tapping screw | |
| Note on materials | RoHS-compliant | | | | | | |
| Housing colour | Black | | | | | | |
| Information on housing materials | PA | | | | | | |



Dimensions Download CAD data → www.festo.com



| Type | B1 | H1 ±0.5 | L1 | L2 | L3 |
|-----------------|-----|------------|------|-----|-----|
| VAVE-L1-1VS2-LP | 9.8 | 28.8 | 12.9 | 5.2 | 6.5 |
| VAVE-L1-1S2-LR | | | 10.8 | | |
| VAVE-L1-1VH2-LP | 9.8 | 28.8 | 12.9 | 5.2 | 6.5 |
| VAVE-L1-H2-LR | | | 10.8 | | |

| Type | B1 | H1 ±0.5 | L1 | L2 | L3 |
|-----------------|-----|------------|-----|-----|-----|
| VAVE-L1-1VS3-LP | 9.8 | 35 | 7.6 | 5.2 | 6.5 |
| VAVE-L1-1S3-LR | | | 7.5 | | |
| VAVE-L1-1VH3-LP | 9.8 | 35 | 7.6 | 5.2 | 6.5 |
| VAVE-L1-1H3-LR | | | 7.5 | | |

Dimensions Download CAD data → www.festo.com



| Type | B1 | H1 ±0.5 | L1 | L2 | L3 |
|-----------------|-----|------------|-----|-----|-----|
| VAVE-L1-1VL1-LP | 9.8 | 28.8 | 7.9 | 0.5 | 6.5 |
| VAVE-L1-1L1-LR | | | | 1 | |
| VAVE-L1-1VL2-LP | | | | 2.5 | |
| VAVE-L1-1L2-LR | | | | 5 | |
| VAVE-L1-1VL3-LP | | | | | |
| VAVE-L1-1L3-LR | | | | | |
| VAVE-L1-1VL4-LP | | | | | |
| VAVE-L1-1L4-LR | | | | | |

| Type | B1 | H1 | H2 ±0.3 | L1 | L2 ±5 | L3 ±0.5 | D1 ∅ |
|-----------------|-----|------|------------|-----|----------|------------|---------|
| VAVE-L1-1VK6-LP | 9.8 | 15.3 | 11.8 | 0.5 | 50 | 28.7 | 1.8 |
| VAVE-L1-1VK7-LP | | | | 1.0 | | | |
| VAVE-L1-1VK8-LP | | | | 2.5 | | | |
| VAVE-L1-1VK9-LP | | | | 5.0 | | | |
| VAVE-L1-1K6-LR | | | | 0.5 | | | |
| VAVE-L1-1K7-LR | | | | 1.0 | | | |
| VAVE-L1-1K8-LR | | | | 2.5 | | | |
| VAVE-L1-1K9-LR | | | | 5.0 | | | |

Solenoid valves VUVG

E-boxes

Dimensions Download CAD data → www.festo.com

E-boxes, R8/R1



| Type | B1 | H1 | H2 | H3 | L1 | L2 | L3 | L4 | D1 |
|-----------------|-----|------|------|------|------|-----|-----|-----|----|
| VAVE-L1-1VR8-LP | 9.8 | 28.7 | 13.7 | 20.2 | 18.4 | 9.9 | 9.7 | 8.6 | M8 |
| VAVE-L1-1VR1-LP | | | | | | | | | |



Ordering data – E-boxes

| Design | Plug | Additional functions | Ambient temperature [°C] | Code | Power | Voltage | Type | | |
|--------|----------------|--------------------------------------------|--------------------------|------|-------|---------|-----------------|-------|-----------------|
| | | | | | [W] | [V DC] | | | |
| | NEBV-H1 ... | Spark arresting, bipolar | -5 ... +50 | H2 | 1 | 12/24 | VAVE-L1-1VH2-LP | | |
| | | Spark arresting, holding current reduction | -5 ... +60 | H2R | 0.35 | 24 | VAVE-L1-1H2-LR | | |
| | NEBV-H1 ... | Spark arresting, bipolar | -5 ... +50 | H3 | 1 | 12/24 | VAVE-L1-1VH3-LP | | |
| | | Spark arresting, holding current reduction | -5 ... +60 | H3R | 0.35 | 24 | VAVE-L1-1H3-LR | | |
| | NEBV-HS ... | Spark arresting, bipolar | -5 ... +50 | S2 | 1 | 12/24 | VAVE-L1-1VS2-LP | | |
| | | Spark arresting, holding current reduction | -5 ... +60 | S2R | 0.35 | 24 | VAVE-L1-1S2-LR | | |
| | NEBV-HS ... | Spark arresting, bipolar | -5 ... +50 | S3 | 1 | 12/24 | VAVE-L1-1VS3-LP | | |
| | | Spark arresting, holding current reduction | -5 ... +60 | S3R | 0.35 | 24 | VAVE-L1-1S3-LR | | |
| | Open cable end | Spark arresting, bipolar | -5 ... +50 | L1 | 1 | 12/24 | VAVE-L1-1VL1-LP | | |
| | | | | L2 | | | VAVE-L1-1VL2-LP | | |
| | | | | L3 | | | VAVE-L1-1VL3-LP | | |
| | | | | L4 | | | VAVE-L1-1VL4-LP | | |
| | | Spark arresting, holding current reduction | -5 ... +60 | L1R | 0.35 | 24 | VAVE-L1-1L1-LR | | |
| | | | | L2R | | | VAVE-L1-1L2-LR | | |
| | | | | L3R | | | VAVE-L1-1L3-LR | | |
| | | | | L4R | | | VAVE-L1-1L4-LR | | |
| | Open cable end | Spark arresting, bipolar | -5 ... +60 | K6 | 1 | 12/24 | VAVE-L1-1VK6-LP | | |
| | | | | K7 | | | VAVE-L1-1VK7-LP | | |
| | | | | K8 | | | VAVE-L1-1VK8-LP | | |
| | | | | K9 | | | VAVE-L1-1VK9-LP | | |
| | | Spark arresting, holding current reduction | -5 ... +60 | K6R | 0.35 | 24 | VAVE-L1-1K6-LR | | |
| | | | | K7R | | | VAVE-L1-1K7-LR | | |
| | | | | K8R | | | VAVE-L1-1K8-LR | | |
| | | | | K9R | | | VAVE-L1-1K9-LR | | |
| | NEBU-M8 ... | Spark arresting, bipolar | -5 ... +60 | R8 | 1 | 12/24 | VAVE-L1-1VR8-LP | | |
| | | Spark arresting, holding current reduction | | R8R | | | 0.35 | 24 | VAVE-L1-1R8-LR |
| | | Spark arresting, bipolar | | R1 | | | 1 | 12/24 | VAVE-L1-1VR1-LP |
| | | Spark arresting, holding current reduction | | R1R | | | | | 0.35 |

Solenoid valves VUVG

Accessories

FESTO

| Ordering data | | | |
|-------------------------------------------------------------------------------------|----------------------------------------------------|------------------|---------------------------------|
| | Description | Cable length [m] | Type |
| Plug socket with cable, not sheathed, open end | | | Technical data → Internet: nebv |
|  | For E-box code H2, H2R or H3, H3R, 2-pin socket | 0.5 | NEBV-H1G2-KN-0.5-N-LE2 |
| | | 1 | NEBV-H1G2-KN-1-N-LE2 |
| | | 2.5 | NEBV-H1G2-KN-2.5-N-LE2 |
| | | 5 | NEBV-H1G2-KN-5-N-LE2 |
| Plug socket with cable, sheathed, open end | | | Technical data → Internet: nebv |
|  | For E-box code H2, H2R or H3, H3R, 2-pin socket | 0.5 | NEBV-H1G2-P-0.5-N-LE2 |
| | | 1 | NEBV-H1G2-P-1-N-LE2 |
| | | 2.5 | NEBV-H1G2-P-2.5-N-LE2 |
| | | 5 | NEBV-H1G2-P-5-N-LE2 |
| Plug socket with cable, not sheathed, open end | | | Technical data → Internet: nebv |
|  | For E-box code S2, S2R or S3, S3R, 2-pin socket | 0.5 | NEBV-HSG2-KN-0.5-N-LE2 |
| | | 1 | NEBV-HSG2-KN-1-N-LE2 |
| | | 2.5 | NEBV-HSG2-KN-2.5-N-LE2 |
| | | 5 | NEBV-HSG2-KN-5-N-LE2 |
| Plug socket with cable, sheathed, open end | | | Technical data → Internet: nebv |
|  | For E-box code S2, S2R or S3, S3R, 2-pin socket | 0.5 | NEBV-HSG2-P-0.5-N-LE2 |
| | | 1 | NEBV-HSG2-P-1-N-LE2 |
| | | 2.5 | NEBV-HSG2-P-2.5-N-LE2 |
| | | 5 | NEBV-HSG2-P-5-N-LE2 |
| Connecting cable, open end | | | Technical data → Internet: nebu |
|  | For E-box code R8, 3-pin, straight socket, M8x1 | 2.5 | NEBU-M8G3-K-2.5-LE3 |
| | | 5 | NEBU-M8G3-K-5-LE3 |
| | For E-box code R1, 4-pin, straight socket, M8x1 | 2.5 | NEBU-M8G4-K-2.5-LE4 |
| | | 5 | NEBU-M8G4-K-5-LE4 |
| Connecting cable, open end | | | Technical data → Internet: nebu |
|  | For E-box code R8, 3-pin, angled socket, M8x1 | 2.5 | NEBU-M8W3-K-2.5-LE3 |
| | | 5 | NEBU-M8W3-K-5-LE3 |
| | For E-box code R1, 4-pin, angled socket, M8x1 | 2.5 | NEBU-M8W4-K-2.5-LE4 |
| | | 5 | NEBU-M8W4-K-5-LE4 |
| Connecting cable | | | |
|  | For E-box code R8, 3-pin, straight socket, M8x1 | 0.5 | NEBU-M8G3-K-0.5-M8G3 |
| | | 1 | NEBU-M8G3-K-1-M8G3 |
| | | 2.5 | NEBU-M8G3-K-2.5-M8G3 |
| | | 5 | NEBU-M8G3-K-5-M8G3 |
| | For E-box code R1, 4-pin, straight socket, M8x1 | 10 | NEBU-M8G3-K-10-M8G3 |
| | | 2.5 | NEBU-M8G3-K-2.5-M8G4 |
| | | 2.5 | NEBU-M8G4-K-2.5-M8G4 |

Solenoid valves VUVG

Accessories


FESTO

| Ordering data | | | |
|-------------------------------------------------------------------------------------|-----------------------------|------------|--------------------------------|
| | Description | | Type |
| Blanking plug | | | Technical data → Internet: b |
|  | For manifold rail and valve | | B-M5-B |
| | | | B-M7 |
| | For manifold rail | | B-1/8 |
| | | | B-1/4 |
| Blanking plug | | | Technical data → Internet: qs |
|  | For valve | | QSC-F-G1/8-I |
| Reducing nipple | | | |
|  | - | | D-M5I-M7A-ISK |
| Fittings | | | Technical data → Internet: qsm |
|  | For tubing ø 3 mm | 100 pieces | QSM-M3-3-I-R-100 |
| | For tubing ø 4 mm | | QSM-M3-4-I-R-100 |
| | For tubing ø 3 mm | | QSM-M5-3-I-R100 |
| | For tubing ø 4 mm | | QSM-M5-4-I-R100 |
| | For tubing ø 6 mm | | QSM-M5-6-I-R100 |
| | For tubing ø 6 mm | | QSM-M7-6-I-R100 |
| | For tubing ø 3 mm | 10 pieces | QSM-M5-3-I |
| | For tubing ø 4 mm | | QSM-M5-4-I |
| | For tubing ø 6 mm | | QSM-M5-6-I |
| | For tubing ø 4 mm | | QSM-M7-4-I |
| | For tubing ø 6 mm | | QSM-M7-6-I |
| | For tubing ø 4 mm | 10 pieces | QS-G1/8-4-I |
| | For tubing ø 6 mm | | QS-G1/8-6-I |
| | For tubing ø 8 mm | | QS-G1/8-8-I |
| | For tubing ø 10 mm | | QS-G1/8-10-I |
| | For tubing ø 6 mm | 10 pieces | QS-G1/4-6-I |
| | For tubing ø 8 mm | | QS-G1/4-8-I |
| | For tubing ø 10 mm | | QS-G1/4-10-I |
| Silencer | | | Technical data → Internet: uc |
|  | For thread M5 | - | U-M5 |
| | For thread M7 | | UC-M7 |
| | For thread G1/8 | | UC-1/8 |
| | For thread G1/4 | | UC-1/4 |

Solenoid valves VUVG

Accessories


FESTO

| Ordering data | | | | | | |
|------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------|--------------------|--------------|----------------|--------------------|---------------------|
| Description | | | | | Type | |
| H-rail Technical data → Internet: nrh | | | | | | |
|  | To EN 60715, 35 x 7.5 (WxH) | 2 m | | | NRH-35-2000 | |
| H-rail mounting Technical data → Internet: vame | | | | | | |
|  | - | 2 pieces | | | VAME-T-M4 | |
| Covers for manual override Technical data → Internet: vmpa | | | | | | |
|  | Covered | 10 pieces | | | VMPA-HBV-B | |
|  | Non-detenting | | | | VMPA-HBT-B | |
| Inscription label holder Technical data → Internet: aslr | | | | | | |
|  | Holder for an inscription label and cover for mounting screw and manual override | | 10 pieces | | ASLR-D-L1 | |
| restrictor | | | | | | |
|  | for M5 valves for setting the exhaust flow rate | nominal value: 9,6 | b value: 0,5 | C value: 0,004 | 10 pieces | VFFG-T-M5-5 |
| | | nominal value:14,6 | b value: 0,5 | C value: 0,005 | | VFFG-T-M5-6 |
| | | nominal value:19,1 | b value: 0,5 | C value: 0,7 | | VFFG-T-M5-7 |
| | | nominal value:26,1 | b value: 0,5 | C value: 0,10 | | VFFG-T-M5-8 |
| | | nominal value:40,8 | b value: 0,5 | C value: 0,14 | | VFFG-T-M5-10 |
| | | nominal value:45,4 | b value: 0,5 | C value: 0,16 | | VFFG-T-M5-12 |
| | | nominal value:67,4 | b value: 0,5 | C value: 0,25 | | VFFG-T-M5-15 |

Valve terminals VTUG with multi-pin plug and fieldbus connection

Key features

FESTO



Innovative

- I-Port interface for fieldbus nodes (CTEU)
- IO-Link mode for direct connection to a higher-level IO-Link master
- Variable multi-pin plug connection using Sub-D or flat cable
- Reversible piston spool valves, up to 24 valve positions
- Reduced power consumption
- Excellent price/performance ratio

Versatile

- Choice of quick plug connectors
- Multiple pressure zones possible
- Sub-D variant and fieldbus connection rated to IP67
- Internal or external pilot air with the same manifold rail possible through the use of blanking plugs
- Sub-base valves with working ports underneath for installation in control cabinets

Reliable

- Sturdy and durable metal components
 - Valves
 - Manifold rails
- Fast troubleshooting thanks to LED display
- Choice of manual override: non-detenting, detenting or covered

Easy to mount

- Easy mounting thanks to captive screws and seal
- Connection technology easy to change via the E-box
- Inscription label holder for labelling

Valve terminal configurator

A valve terminal configurator is available to help you select a suitable valve terminal VTUG. This makes it much easier to order the right product.

Valve terminals VTUG are ordered via an identcode. All valve terminals are supplied fully assembled and individually tested.

This reduces assembly and installation time to a minimum.

Download CAD data → www.festo.com


Ordering system for valve terminal VTUG

→ Internet: vtug


Valve terminals VTUG with multi-pin plug and fieldbus connection

Key features


Sub-base and semi in-line valves



Sub-base valve
VUVG-B...1T1




VUVG-S...1T1
Semi in-line valve



Valve terminal VTUG
with variable electrical connection

Overview



Equipment options

Valve functions

- 2x3/2-way, 5/2-way, 5/3-way valves
- Reversible piston spool valves, up to 24 valve positions


Electrical connection options

- IO-Link mode for direct connection to a higher-level IO-Link master
- Fieldbus node CTEU
- Variable multi-pin plug connection using Sub-D or flat cable

Valve terminals VTUG with multi-pin plug and fieldbus connection


Key features

Basic valves VUVG




- Width 10 and 14 mm
- Semi in-line valves
- Sub-base valves
- 2x3/2-way, 5/2-way and 5/3-way valves

Valve functions




- 2x3/2-way valve, normally open, mechanical spring
- 2x3/2-way valve, normally open, pneumatic spring
- 2x3/2-way valve, normally closed, mechanical spring
- 2x3/2-way valve, normally closed, pneumatic spring
- 2x3/2-way valve, 1x normally closed, 1x normally open, pneumatic spring
- 2x3/2-way valve, 1x normally closed, 1x normally open, mechanical spring
- 5/2-way single solenoid valve, pneumatic/mechanical spring (size 10)
- 5/2-way single solenoid valve, mechanical spring
- 5/2-way single solenoid valve, pneumatic spring (size 14)
- 5/2-way double solenoid valve
- 5/3-way valve, mid-position pressurised
- 5/3-way valve, mid-position exhausted
- 5/3-way valve, mid-position closed

Cover caps for manual override




- Closed cover cap for covering the manual override
- Slotted cover cap for enabling only non-detenting operation of the manual override

Identification holder



- Identification holder ASLR-D-L1 for identifying the individual valves and as a cover for the manual overrides

Inscription label holder




- Inscription label holder ASCF-H-L1-... for identifying the valves on the valve terminal VTUG

Valve terminals VTUG with multi-pin plug and fieldbus connection

Key features

Multi-pin plug connection




The signals are transmitted from the controller to the valve terminal via a pre-assembled or self-assembled multi-wire cable to the multi-pin plug connection,

which substantially reduces installation time. The valve terminal can be equipped with max. 48 solenoid coils.

Versions:

- Sub-D connection
- Flat cable

I-Port interface



Festo-specific interface as a basis for fieldbus nodes (CTEU) or in IO-Link mode for direct connection to a higher-level IO-Link master.

Transmission of communication data and the power supply takes place via an M12 plug on the terminal.

Connection options:

- As an I-Port interface for fieldbus nodes (CTEU)
- In IO-Link mode for direct connection to an IO-Link master

Valve terminal configurator

A valve terminal configurator is available to help you select a suitable valve terminal VTUG. This makes it much easier to order the right product.

Valve terminals VTUG are ordered via an identcode. All valve terminals are supplied fully assembled and individually tested.

This reduces assembly and installation time to a minimum.

Download CAD data → www.festo.com


Ordering system for valve terminal VTUG

- Individual electrical connection
 - Electrical multi-pin plug connection
- Internet: vtug

Valve terminals VTUG with multi-pin plug and fieldbus connection


Key features – Pneumatic components

Manifold rail for semi in-line valves



- For semi in-line valves M5, M7, width 10 mm and G1/8, size 14 mm
- For 2x3/2-way, 5/2-way and 5/3-way valves
- 4 to 24 valve positions with electrical interlinking
- The semi in-line valves are always supplied with external pilot air. The pilot air is set via the manifold rail. A short and a long blanking plug are included with the manifold rail for this purpose.

Manifold rail for sub-base valves




- For sub-base valves M5/M7, width 10 mm and G1/8, width 14 mm
- For 2x3/2-way, 5/2-way and 5/3-way valves
- 4 to 24 valve positions with electrical interlinking
- The sub-base valves are always supplied with external pilot air. The pilot air is set via the manifold rail. A short and a long blanking plug are included with the manifold rail for this purpose.



Note


Pressurisation and exhaust at both ends is recommended for an optimised flow rate in cases where there are multiple valves switching simultaneously.

Blanking plate for vacant position



- Vacant position cover

Supply plate



- For additional air supply and exhaust via a valve position



Note

Supply plate
VABF-L1-14-P3A4-G18-T1
can only be used with G fittings.
R fittings are not permitted.

Separator for pressure zones



- For creating multiple pressure zones in a valve terminal

Valve terminals VTUG with multi-pin plug and fieldbus connection

Key features – Pneumatic components

Creating pressure zones and separating exhaust air

Compressed air is supplied and exhausted via the manifold rail and via supply plates.

The position of the supply plates and duct separations can be freely selected with the VTUG.





Pressure zones are created by isolating the internal supply ducts between the manifold sub-bases by means of appropriate duct separation.

Pressure zone separation can be used for the following ducts:


- Duct 1
- Duct 3
- Duct 5

 Note

- Use a separator if the exhaust air pressures are high
- Use at least one supply plate/supply for each pressure zone
- Pressure zone separation is not possible with pilot air supply (duct 12/14)

| Duct separation | Description |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  | <p>The pressure zones can be freely configured with the VTUG. The following duct separations are possible:</p> <ul style="list-style-type: none"> • Duct 1 closed  |
|  | <ul style="list-style-type: none"> • Duct 1/3/5 closed  |
|  | <ul style="list-style-type: none"> • Duct 3/5 closed  |
| | <p>The number of pressure zones with the VTUG is only limited by the number of valve positions on the manifold rail. Note that each supply plate occupies one valve position.</p> |

Separator VABD



 Separator VABD

 Note

With the VTUG, several pressure zones can be created by mounting separators (VABD). The separators are mounted in the profile using a slotted screwdriver.

Valve terminals VTUG with multi-pin plug and fieldbus connection

Key features – Pneumatic components

Pilot air supply

Internal pilot air supply

Internal pilot air supply can be chosen with an operating pressure in the range 1.5 ... 8 bar, 2.5 ... 8 bar or 3 ... 8 bar (depending on the valve used).

The pilot air supply is branched from duct 1 (compressed air supply) using an internal connection.


External pilot air supply

External pilot air supply is required for vacuum operation and operating pressures >8 bar. The port for external pilot air supply (port 12/14) is located on the manifold rail.

Pilot exhaust air port

The pilot air is exhausted via duct 82/84 of the manifold rail.

Pilot air supply



- 1 Blanking plug, short, with internal pilot air
- 2 Blanking plug for duct 12/14 with internal pilot air
- 3 Blanking plug, long, with external pilot air
- 4 QS fitting for duct 12/14 with external pilot air

The manifold rails have an internal conduit between duct 12/14 and duct 1.

Internal or external pilot air supply is selected by inserting a blanking plug into this conduit.

Valve terminals VTUG with multi-pin plug and fieldbus connection

Key features – Pneumatic components

Operation with different pressures

Vacuum operation

Points to note with 3/2-way valves with pneumatic spring return

The 3/2-way valves are available in a design with two valves in one valve body and with pneumatic spring return. With these valves, the energy for the return movement is obtained from port 1.

Vacuum operation is therefore only possible at port 3 and 5, not at port 1.

With external pilot air supply, vacuum can be connected at port 1, 3, 5 of the 5/2-way and 5/3-way valves.

Reverse operation


The 3/2-way valves with pneumatic spring are not suitable for reverse operation, since at least the minimum pilot pressure must be present in duct 1.



Note

Pressure must be present at port 1.

Pressure deflector (internal pilot air)



- If two different pressures are required.

- Different pressures can be supplied at duct 1, 3 and 5.



Note


- With internal pilot air, the minimum pilot pressure must be adhered to in duct 1
- With 2x3/2-way valves without

spring return, the minimum pilot pressure must always be adhered to in duct 1

Advantages

- Any pressure or vacuum can be connected at duct 3 and 5 both with external and internal pilot air

Vacuum, ejector pulse and normal position




Vacuum, ejector pulse and normal position with internal pilot air can be achieved by connecting vacuum

at duct 3 and pressure for the ejector pulse at duct 1.


Valve terminals VTUG with multi-pin plug and fieldbus connection

Key features – Pneumatic components

Standard nominal flow rate q_{nN} with 5/2-way valve with multiple valves n switched simultaneously, size 10




Standard flow rate q_n as a function of the number of switched valves n , size 14




Pilot pressure p_2 as a function of operating pressure p_1


VUVG-...T32-MZT



VUVG-...T32-AZT



VUVG-...10-M52-RZT-.../VUVG-...14-M52-AZT-...



Valve terminals VTUG with multi-pin plug and fieldbus connection

Key features – Assembly

Valve terminal assembly


Sturdy terminal assembly thanks to:

- Four through-holes for wall mounting
- H-rail mounting

 Note

The thread M5 on the manifold block is provided for earthing the valve terminal.


Wall mounting



The valve terminal VTUG is screwed onto the mounting surface using four M4 screws.

The mounting holes are on the left-hand and right-hand side of the manifold rail.

H-rail mounting



The valve terminal VTUG is attached to the H-rail (see arrow A).

The terminal is then swivelled around the H-rail and secured in place with the clamping component (see arrow B).

The manifold rails can be attached to an H-rail to DIN EN 60715-TH35 using the H-rail mounting kit VAME-T-M4.

The following screws must be used to attach the manifold rails:


- Size 10: M4x30 to DIN 912
- Size 14: M4x40 to DIN 912

Valve terminals VTUG with multi-pin plug and fieldbus connection

Key features – Assembly


Manual override (MO)

MO with automatic return, non-detenting



- 1 Press in the stem of the MO with a pointed object or screwdriver. Pilot valve switches and actuates the main valve.
- 2 Remove the pointed object or screwdriver. Spring force pushes the stem of the MO back. Pilot valve returns to its initial position and so too the single solenoid main valve (not with double solenoid valve code J).


MO set via turning, non-detenting/detenting (standard version)



- 1 Press in the stem of the MO with a pointed object or screwdriver until the valve switches and then turn the stem clockwise by 90° until the stop is reached. Valve remains switched.
- 2 Turn the stem anti-clockwise by 90° until the stop is reached and then remove the pointed object or screwdriver. Spring force pushes the stem of the MO back. Valve returns to its initial position (not with double solenoid valve code J).

Inscription system

Inscription label holder




An inscription label holder ASCF-H-L1 (code TT) can be mounted for labelling the valves. The inscription label holder can be opened for inserting the inscription label and for actuating the manual override. The inscription label holders are available in different sizes depending on the number of valves.

 Note

The inscription label holder covers the manual override of the valves beneath it after mounting (manual override can only be actuated without detent). For this reason, the manual override for these valves must not be engaged/actuated when mounting the inscription label holder.

Identification holder



The identification holder ASLR-D-L1 (code TV) can alternatively be used to label the individual valves. This identification holder is placed directly on the manual override.











 Note

After mounting the holder, the manual override can only be actuated without detent. For this reason, the manual override must not be actuated/engaged when mounting the identification holder.

Valve terminals VTUG with multi-pin plug and fieldbus connection




FESTO

Overview of valve functions

| Valve | Valve code | Description | Valve terminal/ position function order code | Size | | |
|-------------------------------------------------------------------------------------|------------|-------------------------------------------|----------------------------------------------------|-------|------|------|
| | | | | M5/M7 | G1/8 | G1/4 |
| 2x3/2-way valve, normally closed, pneumatic spring | | | | | | |
|  | T32C-A | In-line valve, internal pilot air supply | K | ■ | ■ | ■ |
| 2x3/2-way valve, normally open, pneumatic spring | | | | | | |
|  | T32U-A | Sub-base valve, external pilot air supply | N | ■ | ■ | ■ |
| 2x3/2-way valve, 1x normally open, 1x normally closed, pneumatic spring | | | | | | |
|  | T32H-A | Sub-base valve, external pilot air supply | H | ■ | ■ | ■ |
| 2x3/2-way valve, normally closed, mechanical spring | | | | | | |
|  | T32C-M | Sub-base valve, external pilot air supply | VK | ■ | ■ | ■ |
| 2x3/2-way valve, normally open, mechanical spring | | | | | | |
|  | T32U-M | Sub-base valve, external pilot air supply | VN | ■ | ■ | ■ |
| 2x3/2-way valve, 1x normally open, 1x normally closed, mechanical spring | | | | | | |
|  | T32H-M | Sub-base valve, external pilot air supply | VH | ■ | ■ | ■ |
| 5/2-way double solenoid valve | | | | | | |
|  | B52 | Sub-base valve, external pilot air supply | J | ■ | ■ | ■ |
| 5/2-way single solenoid valve, pneumatic spring | | | | | | |
|  | M52-A | Sub-base valve, external pilot air supply | M | - | ■ | - |
| 5/2-way single solenoid valve, mechanical spring | | | | | | |
|  | M52-M | Sub-base valve, external pilot air supply | A | ■ | ■ | ■ |
| 5/2-way single solenoid valve, pneumatic/mechanical spring | | | | | | |
|  | M52-R | Sub-base valve, external pilot air supply | P | ■ | - | ■ |

Valve terminals VTUG with multi-pin plug and fieldbus connection


Overview of valve functions

| Valve | Valve type code | Description | Valve terminal/ position function order code | Size | | |
|-----------------------------------------------------------------------------------|-----------------|-------------------------------------------|----------------------------------------------------|-------|------|------|
| | | | | M5/M7 | G1/8 | G1/4 |
| 5/3-way valve, mid-position closed | | | | | | |
|  | P53C | Sub-base valve, external pilot air supply | G | ■ | ■ | ■ |
| 5/3-way valve, mid-position pressurised | | | | | | |
|  | P53U | Sub-base valve, external pilot air supply | B | ■ | ■ | ■ |
| 5/3-way valve, mid-position exhausted | | | | | | |
|  | P53E | Sub-base valve, external pilot air supply | E | ■ | ■ | ■ |

Valve terminals VTUG with multi-pin plug and fieldbus connection

Peripherals overview – Semi in-line valves

Valve terminal overview – Semi in-line valves



| Accessories | | | | |
|-------------|-----------------|-------------------|------------------------------------------------------|-------------|
| | Type | Brief description | → Page/Internet | |
| 1 | Manifold rail | VABM-L1-... | For 4 to 10, 12, 14, 16, 20 and 24 valve positions | 108 |
| 2 | H-rail mounting | VAME-T-M4 | 2 pieces for fitting the valve terminal on an H-rail | 122 |
| 3 | H-rail | NRH-35-2000 | For mounting the valve terminal | 122 |
| 4 | Separator | VABD-... | For creating pressure zones | 122 |
| 5 | Blanking plate | VABB-L1-... | For covering an unused valve position | 122 |
| 6 | Supply plate | VABF-L1-... | For air supply port 1 and outlet port 3 and 5 | 122 |
| 7 | Solenoid valve | VUVG-... | Semi in-line valve, 5/2-way single solenoid | 83/87/91/95 |

Valve terminals VTUG with multi-pin plug and fieldbus connection


Peripherals overview – Semi in-line valves

| Accessories | | | | |
|-------------|--------------------------|-------------------|-----------------------------------------------------------------------|-------|
| | Type | Brief description | → Page/Internet | |
| 8 | Cover cap | VMPA-HB...-B | Cover cap for manual override | 122 |
| 9 | Identification holder | ASLR-D-L1 | For inscription label and covering the mounting screw/manual override | 123 |
| 10 | Solenoid valve | VUVG-... | Semi in-line valve, 2x3/2-way, 5/2-way double solenoid and 5/3-way | 83/87 |
| 11 | Silencer | U-... | For outlet port 3 and 5 | 121 |
| 12 | Push-in fitting | QS-... | Push-in fitting for air supply port 1 | 121 |
| 13 | Blanking plug | B-... | For internal/external pilot air | 121 |
| 14 | Push-in fitting | QS-... | For port 2/4 | 121 |
| 15 | Electrical interface | VAEM-L1-S-M3-... | Flat cable | 114 |
| 16 | Electrical interface | VAEM-L1-S-M1-... | Sub-D | 114 |
| 17 | Connecting cable | NEBV-... | Sub-D cable | 114 |
| 18 | I-Port interface | VAEM-L1-S-...-PT | IO-Link | 117 |
| 19 | Plug | SEA-M12-5GS-PG7 | Straight plug for I-Port interface/IO-Link | 117 |
| 20 | Fieldbus | CTEU-... | Fieldbus node | 37 |
| 21 | Power supply socket | NTSD/FBSD | Power supply for fieldbus node CTEU | 121 |
| 22 | Inscription label holder | ASCF-H-L1 | For identifying the valves | 123 |
| 23 | H-rail | CAFM-F1-H | For E-box CAPC | 119 |
| 24 | E-box | CAPC-F1-E-M12 | For connecting a second device with I-Port interface | 119 |
| 25 | Connecting cable | NEBU | - | nebu |

Valve terminals VTUG with multi-pin plug and fieldbus connection

Peripherals overview – Sub-base valves

Valve terminal overview – Sub-base valves



| Accessories | | | | |
|-------------|-----------------------|-------------------|-----------------------------------------------------------------------|-------|
| | Type | Brief description | → Page/Internet | |
| 1 | Manifold rail | VABM-L1-... | For 4 to 10, 12, 14, 16, 20 and 24 valve positions | 108 |
| 2 | H-rail mounting | VAME-T-M4 | 2 pieces for fitting the valve terminal on an H-rail | 122 |
| 3 | H-rail | NRH-35-2000 | For mounting the valve terminal | 122 |
| 4 | Separator | VABD-... | For creating pressure zones | 122 |
| 5 | Blanking plate | VABB-L1-... | For covering an unused valve position | 122 |
| 6 | Supply plate | VABF-L1-... | For air supply port 1 and outlet port 3 and 5 | 122 |
| 7 | Solenoid valve | VUVG- ... | Sub-base valve, 5/2-way single solenoid | 91/95 |
| 8 | Cover cap | VMPA-HB...-B | Cover cap for manual override | 122 |
| 9 | Identification holder | ASLR-D-L1 | For inscription label and covering the mounting screw/manual override | 123 |

Valve terminals VTUG with multi-pin plug and fieldbus connection

Peripherals overview – Sub-base valves

| Accessories | | | | |
|-------------|--------------------------|-------------------|----------------------------------------------------------------|-------|
| | Type | Brief description | → Page/Internet | |
| 10 | Solenoid valve | VUVG- ... | Sub-base valve, 2x3/2-way, 5/2-way double solenoid and 5/3-way | 91/95 |
| 11 | Silencer | U... | For outlet port 3 and 5 | 121 |
| 12 | Push-in fitting | QS... | Push-in fitting for air supply port 1 | 121 |
| 13 | Blanking plug | B-... | For internal/external pilot air | 121 |
| 14 | Push-in fitting | QS... | For port 2/4 | 121 |
| 15 | Electrical interface | VAEM-L1-S-M3-... | Flat cable | 114 |
| 16 | Electrical interface | VAEM-L1-S-M1-... | Sub-D | 114 |
| 17 | Connecting cable | NEBV-... | Sub-D cable | 114 |
| 18 | I-Port interface | VAEM-L1-S-...-PT | IO-Link | 117 |
| 19 | Plug | SEA-M12-5GS-PG7 | Straight plug for I-Port interface/IO-Link | 117 |
| 20 | CTEU | CTEU-... | Fieldbus node | 37 |
| 21 | Power supply socket | NTSD | Power supply for fieldbus node CTEU | 121 |
| 22 | Inscription label holder | ASCF-H-L1 | For identifying the valves | 123 |
| 23 | H-rail | CAFM-F1-H | For E-box CAPC | 119 |
| 24 | E-box | CAPC-F1-E-M12 | For connecting a second device with I-Port interface | 119 |
| 25 | Connecting cable | NEBU | - | nebu |

Valve terminals VTUG with multi-pin plug and fieldbus connection

Technical data – Semi in-line valves M5/M7

Function

2x3/2C, 2x3/2U, 2x3/2H
5/2-way, single solenoid
5/2-way, double solenoid
5/3C, 5/3U, 5/3E

Circuit symbol → page 10

-  - Width 10 mm
-  - Flow rate
130 ... 330 l/min
-  - Voltage
24 V DC



| General technical data | | | | | | | | | | | | |
|--------------------------------|------------------------------------------------------------------------|-----------------|-----------------|-------------------------|-----------------|-----------------|-------------------|----------|------------|-----------------|-----------------|-----------------|
| Valve function | T32-A | | | T32-M | | | M52-R | B52 | M52-M | P53 | | |
| Normal position | C ¹⁾ | U ²⁾ | H ⁴⁾ | C ¹⁾ | U ²⁾ | H ⁴⁾ | – | – | | C ¹⁾ | U ²⁾ | E ³⁾ |
| Stable position | Monostable | | | | | | | Bistable | Monostable | | | |
| Pneumatic spring reset method | Yes | | | No | | | Yes ⁵⁾ | – | No | – | | |
| Mechanical spring reset method | No | | | Yes | | | Yes ⁵⁾ | – | Yes | – | | |
| Vacuum operation at port 1 | No | | | With external pilot air | | | | | | | | |
| Design | Piston spool valve | | | | | | | | | | | |
| Sealing principle | Soft | | | | | | | | | | | |
| Actuation type | Electric | | | | | | | | | | | |
| Type of control | Piloted | | | | | | | | | | | |
| Pilot air supply | External | | | | | | | | | | | |
| Exhaust function | With flow control | | | | | | | | | | | |
| Manual override | Choice of non-detenting/detenting (standard), non-detenting or covered | | | | | | | | | | | |
| Type of mounting | On manifold rail | | | | | | | | | | | |
| Mounting position | Any | | | | | | | | | | | |
| Switching position display | LED | | | | | | | | | | | |
| Standard nominal flow rate M5 | [l/min] | 150 | | | 130 | | | 230 | | 210 | | |
| Standard nominal flow rate M7 | [l/min] | 160 | | | 140 | | | 330 | | 290 | 280 | |
| Flow rate on manifold rail M5 | [l/min] | 150 | | | 130 | | | 230 | | 210 | | |
| Flow rate on manifold rail M7 | [l/min] | 160 | | | 140 | | | 330 | | 290 | 280 | |
| Width | [mm] | 10 | | | | | | | | | | |
| Port 1, 3, 5 | On manifold rail | | | | | | | | | | | |
| Port 2, 4 | VUVG-S10-...-M5 | M5 | | | | | | | | | | |
| Port 2, 4 | VUVG-S10-...-M7 | M7 | | | | | | | | | | |
| Port 12, 14 | On manifold rail | | | | | | | | | | | |
| Product weight | [g] | 59 | | | | | 53 | | 60 | 53 | 58 | |
| Corrosion resistance class | CRC | 2 ⁶⁾ | | | | | | | | | | |

- 1) C = Normally closed
- 2) U = Normally open
- 3) E = Normally exhausted
- 4) H=2x3/2-way valve in one housing with 1x normally closed and 1x normally open
- 5) Combined reset method
- 6) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Valve terminals VTUG with multi-pin plug and fieldbus connection

Technical data – Semi in-line valves M5/M7

| Operating and environmental conditions | | | | | | | |
|----------------------------------------|----------------|-----------------------------------------------------------|---------------------|---------------------|-----------|---------------------|-------------|
| Valve function | | T32-A ¹⁾ | T32-M ³⁾ | M52-R ²⁾ | B52 | M52-M ³⁾ | P53 |
| Operating medium | | Compressed air in accordance with ISO 8573-1:2010 [7:4:4] | | | | | |
| Operating pressure | Internal [bar] | 1.5 ... 8 | 2 ... 8 | 2.5 ... 8 | 1.5 ... 8 | 3 ... 8 | |
| | External [bar] | 1.5 ... 10 | -0.9 ... 10 | | | -0.9 ... 8 | -0.9 ... 10 |
| Pilot pressure ⁴⁾ [bar] | | 1.5 ... 8 | 2 ... 8 | 2.5 ... 8 | 1.5 ... 8 | 3 ... 8 | |
| Ambient temperature [°C] | | -5 ... +60 | | | | | |
| Temperature of medium [°C] | | -5 ... +60 | | | | | |

- 1) Pneumatic spring
- 2) Mixed, pneumatic/mechanical spring
- 3) Mechanical spring
- 4) Minimum pilot pressure 50% of operating pressure

| Electrical data | |
|------------------------------------------|------------------------------------------------------------------------------------------------------|
| Electrical connection | Via manifold rail |
| Operating voltage [V DC] | 24 ±10% |
| Power consumption per valve solenoid [W] | 1/0.4 (after 25 ms) |
| Duty cycle [%] | 100 |
| Protection class to EN 60529 | IP40 as standard (optionally IP67 with Sub-D and IO-Link interface with feature "S8" ¹⁾) |

- 1) S8= IP67 protection class for electrics

| Information on materials | |
|--------------------------|-------------------------|
| Housing | Wrought aluminium alloy |
| Seals | HNBR, NBR |
| Note on materials | RoHS-compliant |


| Valve switching times [ms] | | | | | | | |
|----------------------------|--|---------------------|---------------------|---------------------|-----|---------------------|-----|
| Valve function | | T32-A ¹⁾ | T32-M ³⁾ | M52-R ²⁾ | B52 | M52-M ³⁾ | P53 |
| Switching time on [ms] | | 8 | 10 | 9 | – | 12 | 12 |
| Switching time off [ms] | | 20 | 20 | 21 | – | 30 | 38 |
| Changeover time [ms] | | – | – | – | 9 | – | 16 |

- 1) Pneumatic spring
- 2) Mixed, pneumatic/mechanical spring
- 3) Mechanical spring

Valve terminals VTUG with multi-pin plug and fieldbus connection

Technical data – Semi in-line valves M5/M7

Dimensions – Semi in-line valves M5/M7











 Ports 2 and 4: M5/M7  Mounting screw

| Type | B1 | H1 | H2 | L1 | L2 | L3 | L4 | L5 | L6 | L7 |
|----------------------|------|------|------|------|----|----|------|----|----|----|
| VUVG-S10-...-M5-1T1L | 10.3 | 40.9 | 33.6 | 88.6 | 62 | 47 | 14.7 | 3 | 16 | 12 |
| VUVG-S10-...-M7-1T1L | | | | | | | | | | |

Valve terminals VTUG with multi-pin plug and fieldbus connection

Order code – Semi in-line valves M5/M7

| | | | |
|-------------------------------------------------------------------------------------|---|-----------|-------------|
| VUVG | - | 10 | - |
| Valve design | | | |
| Semi in-line valves | | S | |
| Width | | | |
| 10 mm | | 10 | |
| Valve functions | | | |
|  | | | M52 |
|  | | | B52 |
|  | | | P53C |
|  | | | P53U |
|  | | | P53E |
|  | | | T32C |
|  | | | T32H |
|  | | | T32U |

| | |
|----------------------------------|-----------------------------------------|
| Display | |
| L | LED |
| Electrical connection | |
| T1 | Plug-in |
| Nominal operating voltage | |
| 1 | 24 V DC |
| Pneumatic connection | |
| M5 | M5 |
| M7 | M7 |
| Q3 | Push-in connector 3 mm |
| Q4 | Push-in connector 4 mm |
| QH4 | Push-in connector 4 mm/M7 |
| Q6 | Push-in connector 6 mm |
| QH6 | Push-in connector 6 mm/M7 |
| T14 | Push-in connector 1/4" |
| TH14 | Push-in connector 1/4", M7 |
| T18 | Push-in connector 1/8" |
| T316 | Push-in connector 3/16" |
| TH316 | Push-in connector 3/16", M7 |
| T532 | Push-in connector 5/32" |
| Manual override | |
| H | Non-detenting |
| S | Covered |
| T | Non-detenting, detenting |
| Pilot air | |
| Z | External |
| Reset method | |
| A | Pneumatic spring for 2x3/2-way |
| M | Mechanical spring for M52 and 2x3/2-way |
| R | Pneu./mech. spring for M52 |
| - | With B52 and P53 |

Valve terminals VTUG with multi-pin plug and fieldbus connection

Technical data – Semi in-line valves G1/8

Function

2x3/2C, 2x3/2U, 2x3/2H
5/2-way, single solenoid
5/2-way, double solenoid
5/3C, 5/3U, 5/3E

Circuit symbol → page 10

-  - Width 14 mm
-  - Flow rate
520 ... 630 l/min
-  - Voltage
24 V DC



| General technical data | | | | | | | | | | | | |
|---------------------------------------------|------------------------------------------------------------------------|-----------------|-----------------|-------------------------|-----------------|-----------------|-------|----------|------------|-----------------|-----------------|-----------------|
| Valve function | T32-A | | | T32-M | | | M52-A | B52 | M52-M | P53 | | |
| Normal position | C ¹⁾ | U ²⁾ | H ⁴⁾ | C ¹⁾ | U ²⁾ | H ⁴⁾ | – | – | | C ¹⁾ | U ²⁾ | E ³⁾ |
| Stable position | Monostable | | | | | | | Bistable | Monostable | | | |
| Pneumatic spring reset method | Yes | | | No | | | Yes | – | No | – | | |
| Mechanical spring reset method | No | | | Yes | | | No | – | Yes | – | | |
| Vacuum operation at port 1 | No | | | With external pilot air | | | | | | | | |
| Design | Piston spool valve | | | | | | | | | | | |
| Sealing principle | Soft | | | | | | | | | | | |
| Actuation type | Electric | | | | | | | | | | | |
| Type of control | Piloted | | | | | | | | | | | |
| Pilot air supply | External | | | | | | | | | | | |
| Exhaust function | With flow control | | | | | | | | | | | |
| Manual override | Choice of non-detenting/detenting (standard), non-detenting or covered | | | | | | | | | | | |
| Type of mounting | On manifold rail | | | | | | | | | | | |
| Mounting position | Any | | | | | | | | | | | |
| Switching position display | LED | | | | | | | | | | | |
| Standard nominal flow rate G ^{1/8} | [l/min] | 610 | | | 520 | | | 620 | 630 | 620 | 590 | |
| Flow rate on manifold rail G ^{1/8} | [l/min] | 610 | | | 520 | | | 620 | 630 | 620 | 590 | |
| Width | [mm] | 14 | | | | | | | | | | |
| Port 1, 3, 5 | On manifold rail | | | | | | | | | | | |
| Port 2, 4 | G ^{1/8} | | | | | | | | | | | |
| Port 12, 14 | On manifold rail | | | | | | | | | | | |
| Product weight | [g] | 102 | | | 100 | | | 91 | 98 | 89 | 95 | |
| Corrosion resistance class | CRC | 2 ⁶⁾ | | | | | | | | | | |

- 1) C = Normally closed
- 2) U = Normally open
- 3) E = Normally exhausted
- 4) H=2x3/2-way valve in one housing with 1x normally closed and 1x normally open
- 5) Combined reset method
- 6) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Valve terminals VTUG with multi-pin plug and fieldbus connection

Technical data – Semi in-line valves G1/8

| Operating and environmental conditions | | | | | | | |
|----------------------------------------|----------------|-----------------------------------------------------------|---------------------|---------------------|-----------|---------------------|-------------|
| Valve function | | T32-A ¹⁾ | T32-M ³⁾ | M52-A ¹⁾ | B52 | M52-M ³⁾ | P53 |
| Operating medium | | Compressed air in accordance with ISO 8573-1:2010 [7:4:4] | | | | | |
| Operating pressure | Internal [bar] | 1.5 ... 8 | 2 ... 8 | 2.5 ... 8 | 1.5 ... 8 | 3 ... 8 | |
| | External [bar] | 1.5 ... 10 | -0.9 ... 10 | | | -0.9 ... 8 | -0.9 ... 10 |
| Pilot pressure ⁴⁾ [bar] | | 1.5 ... 8 | 2 ... 8 | 2.5 ... 8 | 1.5 ... 8 | 3 ... 8 | |
| Ambient temperature [°C] | | -5 ... +60 | | | | | |
| Temperature of medium [°C] | | -5 ... +60 | | | | | |

1) Pneumatic spring

3) Mechanical spring

4) Minimum pilot pressure 50% of operating pressure

| Electrical data | |
|------------------------------|---------------------|
| Electrical connection | Via sub-base |
| Operating voltage [V DC] | 24 ±10% |
| Power [W] | 1/0.4 (after 25 ms) |
| Duty cycle [%] | 100 |
| Protection class to EN 60529 | IP67 |

| Information on materials | |
|--------------------------|-------------------------|
| Housing | Wrought aluminium alloy |
| Seals | HNBR, NBR |
| Note on materials | RoHS-compliant |

| Valve switching times [ms] | | | | | | | |
|----------------------------|--|---------------------|---------------------|---------------------|-----|---------------------|-----|
| Valve function | | T32-A ¹⁾ | T32-M ³⁾ | M52-A ¹⁾ | B52 | M52-M ³⁾ | P53 |
| Switching time on [ms] | | 10 | 13 | 13 | – | 10 | 15 |
| Switching time off [ms] | | 29 | 21 | 26 | – | 38 | 42 |
| Changeover time [ms] | | – | – | – | 9 | – | 25 |


1) Pneumatic spring

3) Mechanical spring

Valve terminals VTUG with multi-pin plug and fieldbus connection

Technical data – Semi in-line valves G1/8

Dimensions – Semi in-line valves G1/8











2 Ports 2 and 4: G1/8 6 Mounting screw

| Type | B1 | H1 | H2 | L1 | L2 | L3 | L4 | L5 | L6 | L7 |
|-----------------------|------|------|------|-------|----|------|------|-----|------|----|
| VUVG-S14-...-G18-1T1L | 14.7 | 40.9 | 33.5 | 107.6 | 81 | 66.5 | 14.7 | 2.8 | 24.3 | 18 |

Valve terminals VTUG with multi-pin plug and fieldbus connection

Order code – Semi in-line valves G1/8

| | | | |
|-------------------------------------------------------------------------------------|---|-----------|-------------|
| VUVG | - | 14 | - |
| Valve design | | | |
| Semi in-line valves | | S | |
| Width | | | |
| 14 mm | | 14 | |
| Valve functions | | | |
|  | | | M52 |
|  | | | B52 |
|  | | | P53C |
|  | | | P53U |
|  | | | P53E |
|  | | | T32C |
|  | | | T32H |
|  | | | T32U |

| | |
|----------------------------------|-----------------------------------------|
| Display | |
| L | LED |
| Electrical connection | |
| T1 | Plug-in |
| Nominal operating voltage | |
| 1 | |
| Pneumatic connection | |
| G18 | G1/8 |
| T14 | Push-in connector 1/4" |
| T516 | Push-in connector 5/16" |
| Q4 | Push-in connector 4 mm |
| Q6 | Push-in connector 6 mm |
| Q8 | Push-in connector 8 mm/G1/8 |
| Manual override | |
| H | Non-detenting |
| S | Covered |
| T | Non-detenting, detenting |
| Pilot air | |
| Z | External |
| Reset method | |
| A | Pneumatic spring for M52 and 2x3/2-way |
| M | Mechanical spring for M52 and 2x3/2-way |
| - | With B52 and P53 |

Valve terminals VTUG with multi-pin plug and fieldbus connection

Technical data – Sub-base valves M5/M7

Function

2x3/2C, 2x3/2U, 2x3/2H
5/2-way, single solenoid
5/2-way, double solenoid
5/3C, 5/3U, 5/3E

Circuit symbol → page 10

-  - Width 10 mm
-  - Flow rate
130 ... 300 l/min
-  - Voltage
24 V DC



| General technical data | | | | | | | | | | | | |
|-------------------------------------------|------------------------------------------------------------------------|-----------------|-----------------|-------------------------|-----------------|-----------------|-------------------|----------|-------|-----------------|-----------------|-----------------|
| Valve function | T32-A | | | T32-M | | | M52-R | B52 | M52-M | P53 | | |
| Normal position | C ¹⁾ | U ²⁾ | H ⁴⁾ | C ¹⁾ | U ²⁾ | H ⁴⁾ | – | – | | C ¹⁾ | U ²⁾ | E ³⁾ |
| Stable position | Monostable | | | | | | | Bistable | | Monostable | | |
| Pneumatic spring reset method | Yes | | | No | | | Yes ⁵⁾ | – | No | – | | |
| Mechanical spring reset method | No | | | Yes | | | Yes ⁵⁾ | – | Yes | – | | |
| Vacuum operation at port 1 | No | | | With external pilot air | | | | | | | | |
| Design | Piston spool valve | | | | | | | | | | | |
| Sealing principle | Soft | | | | | | | | | | | |
| Actuation type | Electric | | | | | | | | | | | |
| Type of control | Piloted | | | | | | | | | | | |
| Pilot air supply | External | | | | | | | | | | | |
| Exhaust function | With flow control | | | | | | | | | | | |
| Manual override | Choice of non-detenting/detenting (standard), non-detenting or covered | | | | | | | | | | | |
| Type of mounting | On manifold rail | | | | | | | | | | | |
| Mounting position | Any | | | | | | | | | | | |
| Switching position display | LED | | | | | | | | | | | |
| Standard nominal flow rate M5/M7 | [l/min] | 160 | | | 140 | | | 300 | | 260 | | |
| Flow rate on manifold rail M5, front | [l/min] | 150 | | | 130 | | | 220 | | 200 | | |
| Flow rate on manifold rail M7, front | [l/min] | 160 | | | 140 | | | 270 | | 240 | 250 | |
| Flow rate on manifold rail M7, underneath | [l/min] | 160 | | | 140 | | | 300 | | 260 | | |
| Width | [mm] | 10 | | | | | | | | | | |
| Port 1, 3, 5 | On manifold rail | | | | | | | | | | | |
| Port 2, 4 | M5/M7 | | | | | | | | | | | |
| Port 12, 14 | On manifold rail | | | | | | | | | | | |
| Product weight | [g] | 59 | | | | | 53 | | 60 | 53 | 58 | |
| Corrosion resistance class | CRC | 2 ⁶⁾ | | | | | | | | | | |

- 1) C = Normally closed
- 2) U = Normally open
- 3) E = Normally exhausted
- 4) H=2x3/2-way valve in one housing with 1x normally closed and 1x normally open
- 5) Combined reset method
- 6) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Valve terminals VTUG with multi-pin plug and fieldbus connection

Technical data – Sub-base valves M5/M7

| Operating and environmental conditions | | | | | | | |
|----------------------------------------|----------------|-----------------------------------------------------------|---------------------|---------------------|-----------|---------------------|-------------|
| Valve function | | T32-A ¹⁾ | T32-M ³⁾ | M52-R ²⁾ | B52 | M52-M ³⁾ | P53 |
| Operating medium | | Compressed air in accordance with ISO 8573-1:2010 [7:4:4] | | | | | |
| Operating pressure | Internal [bar] | 1.5 ... 8 | 2 ... 8 | 2.5 ... 8 | 1.5 ... 8 | 3 ... 8 | |
| | External [bar] | 1.5 ... 10 | -0.9 ... 10 | | | -0.9 ... 8 | -0.9 ... 10 |
| Pilot pressure ⁴⁾ [bar] | | 1.5 ... 8 | 2 ... 8 | 2.5 ... 8 | 1.5 ... 8 | 3 ... 8 | |
| Ambient temperature [°C] | | -5 ... +60 | | | | | |
| Temperature of medium [°C] | | -5 ... +60 | | | | | |

- 1) Pneumatic spring
- 2) Mixed, pneumatic/mechanical spring
- 3) Mechanical spring
- 4) Minimum pilot pressure 50% of operating pressure

| Electrical data | |
|------------------------------------------|------------------------------------------------------------------------------------------------------|
| Electrical connection | Via manifold rail |
| Operating voltage [V DC] | 24 ±10% |
| Power consumption per valve solenoid [W] | 1/0.4 (after 25 ms) |
| Duty cycle [%] | 100 |
| Protection class to EN 60529 | IP40 as standard (optionally IP67 with Sub-D and IO-Link interface with feature "S8" ¹⁾) |

- 1) S8= IP67 protection class for electrics

| Information on materials | |
|--------------------------|-------------------------|
| Housing | Wrought aluminium alloy |
| Seals | HNBR, NBR |
| Note on materials | RoHS-compliant |


| Valve switching times [ms] | | | | | | | |
|----------------------------|--|---------------------|---------------------|---------------------|-----|---------------------|-----|
| Valve function | | T32-A ¹⁾ | T32-M ³⁾ | M52-R ²⁾ | B52 | M52-M ³⁾ | P53 |
| Switching time on [ms] | | 8 | 10 | 9 | – | 12 | 12 |
| Switching time off [ms] | | 20 | 20 | 21 | – | 30 | 38 |
| Changeover time [ms] | | – | – | – | 9 | – | 16 |

- 1) Pneumatic spring
- 2) Mixed, pneumatic/mechanical spring
- 3) Mechanical spring

Valve terminals VTUG with multi-pin plug and fieldbus connection

Technical data – Sub-base valves M5/M7

Dimensions – Sub-base valves M5/M7











 Mounting screw

| Type | B1 | H1 | H2 | L1 | L2 | L3 | L4 | L5 |
|---------------------|------|------|------|------|----|----|------|----|
| VUVG-B10-...-F-1T1L | 10.3 | 40.9 | 33.6 | 88.6 | 62 | 47 | 14.7 | 3 |

Valve terminals VTUG with multi-pin plug and fieldbus connection

Order code – Sub-base valves M5/M7

| | | | |
|-------------------------------------------------------------------------------------|---|-----------|-------------|
| VUVG | - | 10 | - |
| Valve design | | | |
| Sub-base valves | | B | |
| Width | | | |
| 10 mm | | 10 | |
| Valve functions | | | |
|  | | | M52 |
|  | | | B52 |
|  | | | P53C |
|  | | | P53U |
|  | | | P53E |
|  | | | T32C |
|  | | | T32H |
|  | | | T32U |

| | |
|----------------------------------|-----------------------------------------|
| Display | |
| L | LED |
| Electrical connection | |
| T1 | Plug-in |
| Nominal operating voltage | |
| 1 | 24 V DC |
| Pneumatic connection | |
| F | Flange/sub-base |
| Manual override | |
| H | Non-detenting |
| S | Covered |
| T | Non-detenting, detenting |
| Pilot air | |
| Z | External |
| Reset method | |
| A | Pneumatic spring for 2x3/2-way |
| M | Mechanical spring for M52 and 2x3/2-way |
| R | Pneu./mech. spring for M52 |
| - | With B52 and P53 |

Valve terminals VTUG with multi-pin plug and fieldbus connection

Technical data – Sub-base valves G1/8

Function

2x3/2C, 2x3/2U, 2x3/2H
5/2-way, single solenoid
5/2-way, double solenoid
5/3C, 5/3U, 5/3E

Circuit symbol → page 10

-  - Width 14 mm
-  - Flow rate
440 ... 560 l/min
-  - Voltage
24 V DC



| General technical data | | | | | | | | | | | | |
|--------------------------------------------|------------------------------------------------------------------------|-----------------|-----------------|-------------------------|-----------------|-----------------|-------|----------|------------|-----------------|-----------------|-----------------|
| Valve function | T32-A | | | T32-M | | | M52-A | B52 | M52-M | P53 | | |
| Normal position | C ¹⁾ | U ²⁾ | H ⁴⁾ | C ¹⁾ | U ²⁾ | H ⁴⁾ | – | – | | C ¹⁾ | U ²⁾ | E ³⁾ |
| Stable position | Monostable | | | | | | | Bistable | Monostable | | | |
| Pneumatic spring reset method | Yes | | | No | | | Yes | – | No | – | | |
| Mechanical spring reset method | No | | | Yes | | | No | – | Yes | – | | |
| Vacuum operation at port 1 | No | | | With external pilot air | | | | | | | | |
| Design | Piston spool valve | | | | | | | | | | | |
| Sealing principle | Soft | | | | | | | | | | | |
| Actuation type | Electric | | | | | | | | | | | |
| Type of control | Piloted | | | | | | | | | | | |
| Pilot air supply | External | | | | | | | | | | | |
| Exhaust function | With flow control | | | | | | | | | | | |
| Manual override | Choice of non-detenting/detenting (standard), non-detenting or covered | | | | | | | | | | | |
| Type of mounting | On manifold rail | | | | | | | | | | | |
| Mounting position | Any | | | | | | | | | | | |
| Switching position display | LED | | | | | | | | | | | |
| Standard nominal flow rate G18 | [l/min] | 530 | | | 470 | | | 550 | 560 | 550 | 510 | |
| Flow rate on manifold rail G18, front | [l/min] | 490 | | | 440 | | | 500 | 510 | 500 | 470 | |
| Flow rate on manifold rail G18, underneath | [l/min] | 530 | | | 470 | | | 550 | 560 | 550 | 510 | |
| Width | [mm] | 14 | | | | | | | | | | |
| Port 1, 3, 5 | On manifold rail | | | | | | | | | | | |
| Port 2, 4 | G1/8 | | | | | | | | | | | |
| Port 12, 14 | On manifold rail | | | | | | | | | | | |
| Product weight | [g] | 102 | | | 100 | | | 91 | 98 | 89 | 95 | |
| Corrosion resistance class | CRC | 2 ⁶⁾ | | | | | | | | | | |

- 1) C = Normally closed
- 2) U = Normally open
- 3) E = Normally exhausted
- 4) H=2x3/2-way valve in one housing with 1x normally closed and 1x normally open
- 5) Combined reset method
- 6) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Valve terminals VTUG with multi-pin plug and fieldbus connection

Technical data – Sub-base valves G1/8

| Operating and environmental conditions | | | | | | | |
|----------------------------------------|----------------|-----------------------------------------------------------|---------------------|---------------------|-----------|---------------------|-------------|
| Valve function | | T32-A ¹⁾ | T32-M ³⁾ | M52-A ¹⁾ | B52 | M52-M ³⁾ | P53 |
| Operating medium | | Compressed air in accordance with ISO 8573-1:2010 [7:4:4] | | | | | |
| Operating pressure | Internal [bar] | 1.5 ... 8 | 2 ... 8 | 2.5 ... 8 | 1.5 ... 8 | 3 ... 8 | |
| | External [bar] | 1.5 ... 10 | -0.9 ... 10 | | | -0.9 ... 8 | -0.9 ... 10 |
| Pilot pressure ⁴⁾ [bar] | | 1.5 ... 8 | 2 ... 8 | 2.5 ... 8 | 1.5 ... 8 | 3 ... 8 | |
| Ambient temperature [°C] | | -5 ... +60 | | | | | |
| Temperature of medium [°C] | | -5 ... +60 | | | | | |

- 1) Pneumatic spring
 3) Mechanical spring
 4) Minimum pilot pressure 50% of operating pressure

| Electrical data | | |
|------------------------------|---------------------|--|
| Electrical connection | Via sub-base | |
| Operating voltage [V DC] | 24 ±10% | |
| Power [W] | 1/0.4 (after 25 ms) | |
| Duty cycle [%] | 100 | |
| Protection class to EN 60529 | IP67 | |

| Information on materials | |
|--------------------------|-------------------------|
| Housing | Wrought aluminium alloy |
| Seals | HNBR, NBR |
| Note on materials | RoHS-compliant |


| Valve switching times [ms] | | | | | | | |
|----------------------------|--|---------------------|---------------------|---------------------|-----|---------------------|-----|
| Valve function | | T32-A ¹⁾ | T32-M ²⁾ | M52-A ¹⁾ | B52 | M52-M ²⁾ | P53 |
| Switching time on [ms] | | 10 | 13 | 13 | – | 10 | 15 |
| Switching time off [ms] | | 29 | 21 | 26 | – | 38 | 42 |
| Changeover time [ms] | | – | – | – | 9 | – | 25 |

- 1) Pneumatic spring
 2) Mechanical spring

Valve terminals VTUG with multi-pin plug and fieldbus connection

Technical data – Sub-base valves G1/8

Dimensions – Sub-base valves G1/8



6 Mounting screw

| Type | B1 | H1 | H2 | L1 | L2 | L3 | L4 | L5 |
|---------------------|------|------|------|-------|----|------|------|-----|
| VUVG-B14-...-F-1T1L | 14.7 | 40.9 | 33.5 | 107.6 | 81 | 66.5 | 14.7 | 2.8 |

Valve terminals VTUG with multi-pin plug and fieldbus connection

FESTO

Technical data – Manifold rail VABM


| General technical data | | |
|--------------------------------|-----------------------|-----------------|
| Manifold rail | Size 10 | Size 14 |
| Type code | VABM | |
| Grid dimension [mm] | 10.5 | 16 |
| Mounting position | Any | |
| Connection type | Semi in-line/sub-base | |
| Max. number of valve positions | 24 | |
| Pneumatic interfaces | | |
| Port 12/14 | M5 | |
| Port 82/84 | M5 | |
| Port 2, 4 | M5/M7 | G $\frac{1}{8}$ |
| Port 1, 3, 5 | G $\frac{1}{8}$ | G $\frac{1}{4}$ |
| Storage temperature [°C] | -20 ... 60 | |

| Information on materials | |
|--------------------------|-------------------------|
| Manifold rail material | Wrought aluminium alloy |
| Note on materials | RoHS-compliant |

Dimensions – Example of a valve terminal with I-Port interface

Download CAD data → www.festo.com

Outlet on top



Valve terminals VTUG with multi-pin plug and fieldbus connection

Technical data – Manifold rail VABM

| Type | No. of valve positions | Size 10 | | | | | | | | | | | | | | | | | |
|------|------------------------|---------|----|------|------|------|-----|----|------|------|-------|------|----|------|------|------|------|------|--|
| | | B1 | B2 | B3 | B4 | B5 | B6 | B7 | B8 | D1 Ø | H1 | H2 | H3 | H4 | H5 | H6 | H7 | H8 | |
| VABM | 4-24 | 91.5 | 54 | 52.4 | 41.5 | 25.6 | 9.8 | 16 | 17.7 | 4.5 | 102.3 | 77.1 | 67 | 56.1 | 54.1 | 15.2 | 11.5 | 15.5 | |

| Type | No. of valve positions | Size 10 | | | | | | | | | | |
|------|------------------------|---------|-----|------|-----|------|------|-----|-----|----|----|------|
| | | H9 | H10 | H11 | H12 | L4 | L5 | L6 | L7 | L8 | L9 | L10 |
| VABM | 4-24 | 12.4 | 5.5 | 54.8 | 4.8 | 10.5 | 57.3 | 2.5 | 4.5 | 36 | 20 | 42.5 |

| Type | No. of valve positions | Size 14 | | | | | | | | | | | | | | | | | |
|------|------------------------|---------|----|------|------|------|----|----|------|------|-------|------|------|------|------|------|------|------|--|
| | | B1 | B2 | B3 | B4 | B5 | B6 | B7 | B8 | D1 Ø | H1 | H2 | H3 | H4 | H5 | H6 | H7 | H8 | |
| VABM | 4-24 | 110 | 70 | 59.3 | 56.5 | 36.5 | 16 | 20 | 26.5 | 4.5 | 113.1 | 95.1 | 77.7 | 68.6 | 61.3 | 18.7 | 15.7 | 28.7 | |

| Type | No. of valve positions | Size 14 | | | | | | | | | | |
|------|------------------------|---------|------|------|-----|----|------|----|----|----|------|------|
| | | H9 | H10 | H11 | H12 | L4 | L5 | L6 | L7 | L8 | L9 | L10 |
| VABM | 4-24 | 13.2 | 23.7 | 54.8 | 5.1 | 16 | 60.6 | 2 | 5 | 10 | 25.5 | 42.5 |

| Type | No. of valve positions | Size 10 | | | | | | Size 14 | | | | | |
|------|------------------------|---------|-------|-------|-----|-----|-----|---------|-----|-----|-----|-----|-----|
| | | L1 | L2 | L3 | L1 | L2 | L3 | L1 | L2 | L3 | L1 | L2 | L3 |
| VABM | 4 | 103 | 94 | 31.5 | 128 | 118 | 48 | 128 | 118 | 48 | 128 | 118 | 48 |
| | 5 | 113.5 | 104.5 | 42 | 144 | 134 | 64 | 144 | 134 | 64 | 144 | 134 | 64 |
| | 6 | 124 | 115 | 52.5 | 160 | 150 | 80 | 160 | 150 | 80 | 160 | 150 | 80 |
| | 7 | 134.5 | 125.5 | 63 | 176 | 166 | 96 | 176 | 166 | 96 | 176 | 166 | 96 |
| | 8 | 145 | 136 | 73.5 | 192 | 182 | 112 | 192 | 182 | 112 | 192 | 182 | 112 |
| | 9 | 155.5 | 146.5 | 84 | 208 | 198 | 128 | 208 | 198 | 128 | 208 | 198 | 128 |
| | 10 | 166 | 157 | 94.5 | 224 | 214 | 144 | 224 | 214 | 144 | 224 | 214 | 144 |
| | 12 | 187 | 178 | 115.5 | 256 | 246 | 176 | 256 | 246 | 176 | 256 | 246 | 176 |
| | 16 | 229 | 220 | 157.5 | 320 | 310 | 240 | 320 | 310 | 240 | 320 | 310 | 240 |
| 20 | 271 | 262 | 199.5 | 384 | 374 | 304 | 384 | 374 | 304 | 384 | 374 | 304 | |
| 24 | 313 | 304 | 241.5 | 448 | 438 | 368 | 448 | 438 | 368 | 448 | 438 | 368 | |


Valve terminals VTUG with multi-pin plug and fieldbus connection

Technical data – Manifold rail VABM

Dimensions – Example of a valve terminal with I-Port interface

Download CAD data → www.festo.com

Outlet on the side



| Type | No. of valve positions | Size 10 | | | | | | | | | | | | | | | | |
|------|------------------------|---------|----|------|------|------|-----|----|------|------|-------|------|----|------|------|------|------|------|
| | | B1 | B2 | B3 | B4 | B5 | B6 | B7 | B8 | D1 Ø | H1 | H2 | H3 | H4 | H5 | H6 | H7 | H8 |
| VABM | 4-24 | 91.5 | 54 | 52.4 | 41.5 | 25.6 | 9.8 | 16 | 17.7 | 4.5 | 102.3 | 77.1 | 67 | 56.1 | 54.1 | 15.2 | 11.5 | 15.5 |

| Type | No. of valve positions | Size 10 | | | | | | | | | | | |
|------|------------------------|---------|-----|------|------|-----|------|-------|-----|-----|----|----|------|
| | | H9 | H10 | H11 | H12 | H13 | L4 | L5 | L6 | L7 | L8 | L9 | L10 |
| VABM | 4-24 | 12.4 | 5.5 | 40.8 | 10.1 | 5.1 | 10.5 | 106.8 | 2.5 | 4.5 | 36 | 75 | 47.1 |

| Type | No. of valve positions | Size 14 | | | | | | | | | | | | | | | | |
|------|------------------------|---------|----|------|------|------|----|----|------|------|-------|------|------|------|------|------|------|------|
| | | B1 | B2 | B3 | B4 | B5 | B6 | B7 | B8 | D1 Ø | H1 | H2 | H3 | H4 | H5 | H6 | H7 | H8 |
| VABM | 4-24 | 110 | 70 | 59.3 | 56.5 | 36.5 | 16 | 20 | 26.5 | 4.5 | 113.1 | 95.1 | 77.7 | 68.6 | 61.3 | 18.7 | 15.7 | 28.7 |

| Type | No. of valve positions | Size 14 | | | | | | | | | | | |
|------|------------------------|---------|------|------|------|-----|----|-------|----|----|----|----|------|
| | | H9 | H10 | H11 | H12 | H13 | L4 | L5 | L6 | L7 | L8 | L9 | L10 |
| VABM | 4-24 | 13.2 | 23.7 | 40.8 | 10.1 | 5.1 | 16 | 110.1 | 2 | 5 | 10 | 75 | 47.1 |

Valve terminals VTUG with multi-pin plug and fieldbus connection

Technical data – Manifold rail VABM

| Type | No. of valve positions | Size 10 | | | Size 14 | | |
|------|------------------------|---------|-------|-------|---------|-------|-----|
| | | L1 | L2 | L3 | L1 | L2 | L3 |
| VABM | 4 | 152.5 | 143.5 | 31.5 | 177.5 | 167.5 | 48 |
| | 5 | 163 | 154 | 42 | 193.5 | 183.5 | 64 |
| | 6 | 173.5 | 164.5 | 52.5 | 209.5 | 199.5 | 80 |
| | 7 | 184 | 175 | 63 | 225.5 | 215.5 | 96 |
| | 8 | 194.5 | 185.5 | 73.5 | 241.5 | 231.5 | 112 |
| | 9 | 205 | 196 | 84 | 257.5 | 247.5 | 128 |
| | 10 | 215.5 | 206.5 | 94.5 | 273.5 | 263.5 | 144 |
| | 12 | 236.5 | 227.5 | 115.5 | 305.5 | 295.5 | 176 |
| | 16 | 278.5 | 269.5 | 157.5 | 369.5 | 359.5 | 240 |
| | 20 | 321 | 311.5 | 199.5 | 433.5 | 423.5 | 304 |
| | 24 | 362.5 | 353.5 | 241.5 | 497.5 | 487.5 | 368 |


Valve terminals VTUG with multi-pin plug and fieldbus connection

Dimensions – Example of a valve terminal


Dimensions – Front manifold rail

Download CAD data → www.festo.com

Size 10, I-Port interface, outlet on top




Size 14, I-Port interface, outlet on top



Dimensions – Front manifold rail

Download CAD data → www.festo.com

Size 10/14, I-Port interface, outlet on the side



| Type | Manifold rail with I-Port interface, outlet on top | | | | |
|-----------------|----------------------------------------------------|-----|------|------|------|
| | H1 | H2 | L4 | L5 | L6 |
| Connection M7 | 17.6 | 5.4 | 57.3 | 10.5 | 52.3 |
| Connection M5 | | | | | 53.2 |
| Connection G1/8 | 25.8 | 8.8 | 58.5 | 16 | 54 |

| Type | Manifold rail with I-Port interface, outlet on the side | | | | |
|-----------------|---------------------------------------------------------|-----|-------|------|-------|
| | H1 | H2 | L4 | L5 | L6 |
| Connection M7 | 17.6 | 5.4 | 106.8 | 10.5 | 101.8 |
| Connection M5 | | | | | 102.7 |
| Connection G1/8 | 25.8 | 8.8 | 108 | 16 | 103.5 |

| Type | No. of valve positions | Size 10 | | Size 14 | |
|------|------------------------|---------|-----|---------|-----|
| | | L3 | L6 | L3 | L6 |
| VABM | 4 | 31.5 | 48 | 48 | 64 |
| | 5 | 42 | 64 | 64 | 80 |
| | 6 | 52.5 | 80 | 80 | 96 |
| | 7 | 63 | 96 | 96 | 112 |
| | 8 | 73.5 | 112 | 112 | 128 |
| | 9 | 84 | 128 | 128 | 144 |
| | 10 | 94.5 | 144 | 144 | 176 |
| | 12 | 115.5 | 176 | 176 | 240 |
| | 16 | 157.5 | 240 | 240 | 304 |
| | 20 | 199.5 | 304 | 304 | 368 |
| 24 | 241.5 | 368 | 368 | | |


Valve terminals VTUG with multi-pin plug and fieldbus connection

Dimensions – Example of control cabinet installation

Dimensions – Manifold rail, outlet underneath

Download CAD data → www.festo.com

Control cabinet installation



Note

Dimensions of the manifold rail with I-Port interface, outlet on side for control cabinet installation (→ 105)

- 1** Ports 1, 3 and 5: G $\frac{3}{8}$ /G $\frac{1}{4}$ (at both ends)
- 2** Ports 2 and 4: M5/M7/G $\frac{1}{8}$ (at both ends)
- 3** Ports 12/14: M5 (at both ends)
- 4** Ports 82/84: M5 (at both ends)
- 5** Mounting holes, outlet direction underneath: M4x8

| Type | Manifold rail with I-Port interface, outlet on top, size 10 | | | | | | | | | | |
|------|-------------------------------------------------------------|------|----|----|----|------|------|------|------|------|-----|
| | B1 | B2 | B3 | B4 | B5 | L4 | L5 | L6 | L7 | L8 | L9 |
| VABM | 41 | 31.8 | 27 | 20 | 13 | 58.8 | 10.5 | 55.7 | 42.3 | 32.3 | 4.5 |

| Type | Manifold rail with I-Port interface, outlet on top, size 14 | | | | | | | | | | |
|------|-------------------------------------------------------------|------|------|------|----|------|----|------|----|----|----|
| | B1 | B2 | B3 | B4 | B5 | L4 | L5 | L6 | L7 | L8 | L9 |
| VABM | 53.5 | 45.1 | 35.2 | 27.8 | 17 | 58.5 | 16 | 58.5 | 43 | 33 | 5 |

| Type | No. of valve positions | Size 10 | | | Size 14 | | |
|------|------------------------|----------|----------|-------|---------|-----|-----|
| | | L1 +5 | L2 +5 | L3 | L1 | L2 | L3 |
| VABM | 4 | 103 | 94 | 31.5 | 128 | 118 | 48 |
| | 5 | 113.5 | 104.5 | 42 | 144 | 134 | 64 |
| | 6 | 124 | 115 | 52.5 | 160 | 150 | 80 |
| | 7 | 134.5 | 125.5 | 63 | 176 | 166 | 96 |
| | 8 | 145 | 136 | 73.5 | 192 | 182 | 112 |
| | 9 | 155.5 | 146.5 | 84 | 208 | 198 | 128 |
| | 10 | 166 | 157 | 94.5 | 224 | 214 | 144 |
| | 12 | 187 | 178 | 115.5 | 256 | 246 | 176 |
| | 16 | 229 | 220 | 157.5 | 320 | 310 | 240 |
| | 20 | 271 | 262 | 199.5 | 384 | 374 | 304 |
| 24 | 313 | 304 | 241.5 | 448 | 438 | 368 | |

Valve terminals VTUG with multi-pin plug and fieldbus connection

FESTO

Dimensions


| Type | Manifold rail with I-Port interface, outlet on the side, size 10 | | | | | | | | | | |
|------|------------------------------------------------------------------|------|----|----|----|-------|------|-------|------|------|-----|
| | B1 | B2 | B3 | B4 | B5 | L4 | L5 | L6 | L7 | L8 | L9 |
| VABM | 41 | 31.8 | 27 | 20 | 13 | 108.3 | 10.5 | 105.2 | 91.8 | 81.8 | 4.5 |

| Type | Manifold rail with I-Port interface, outlet on the side, size 14 | | | | | | | | | | |
|------|------------------------------------------------------------------|------|------|------|----|-----|----|-----|------|------|----|
| | B1 | B2 | B3 | B4 | B5 | L4 | L5 | L6 | L7 | L8 | L9 |
| VABM | 53.5 | 45.1 | 35.2 | 27.8 | 17 | 108 | 16 | 108 | 92.5 | 82.5 | 5 |


| Type | No. of valve positions | Manifold rail with I-Port interface, outlet on the side size 10 | | | Manifold rail with I-Port interface, outlet on the side size 14 | | |
|------|------------------------|-----------------------------------------------------------------|----------|-------|-----------------------------------------------------------------|-------|-----|
| | | L1 +5 | L2 +5 | L3 | L1 | L2 | L3 |
| VABM | 4 | 152.5 | 143.5 | 31.5 | 177.5 | 167.5 | 48 |
| | 5 | 163 | 154 | 42 | 193.5 | 183.5 | 64 |
| | 6 | 173.5 | 164.5 | 52.5 | 209.5 | 199.5 | 80 |
| | 7 | 184 | 175 | 63 | 225.5 | 215.5 | 96 |
| | 8 | 194.5 | 185.5 | 73.5 | 241.5 | 231.5 | 112 |
| | 9 | 205 | 196 | 84 | 257.5 | 247.5 | 128 |
| | 10 | 215.5 | 206.5 | 94.5 | 273.5 | 263.5 | 144 |
| | 12 | 236.5 | 227.5 | 115.5 | 305.5 | 295.5 | 176 |
| | 16 | 278.5 | 269.5 | 157.5 | 369.5 | 359.5 | 240 |
| | 20 | 320.5 | 311.5 | 199.5 | 433.5 | 423.5 | 304 |
| | 24 | 362.5 | 353.5 | 241.5 | 497.5 | 487.5 | 368 |

Dimensions – Recess for control cabinet installation, outlet underneath, size 10

Up to 8 valves



9 valves or more



| Type | B1 | B2 | L1 | L2 |
|--------------------|------|-----|-------|----|
| VABM-L--10...G18-4 | 52.7 | 0.5 | 86 | 2 |
| VABM-L--10...G18-5 | | | 96.5 | |
| VABM-L--10...G18-6 | | | 107 | |
| VABM-L--10...G18-7 | | | 117.5 | |
| VABM-L--10...G18-8 | | | 128 | |


| Type | B1 | B2 | B3 | B4 | L1 | L2 | L3 |
|---------------------|------|-----|------|------|-------|----|----|
| VABM-L--10...G18-9 | 52.7 | 0.5 | 47.2 | 15.4 | 138.5 | 2 | 44 |
| VABM-L--10...G18-10 | | | | | 149 | | |
| VABM-L--10...G18-12 | | | | | 170 | | |
| VABM-L--10...G18-16 | | | | | 212 | | |
| VABM-L--10...G18-20 | | | | | 254 | | |
| VABM-L--10...G18-24 | | | | | 296 | | |

Valve terminals VTUG with multi-pin plug and fieldbus connection


Dimensions

Dimensions – Recess for control cabinet installation, outlet underneath, size 14

Up to 7 valves



8 valves or more




| Type | B1 | B2 | L1 | L2 |
|-------------------|------|----|-------|----|
| VABM-L-14...G14-4 | 59.3 | 1 | 130.9 | |
| VABM-L-14...G14-5 | | | 119.9 | |
| VABM-L-14...G14-6 | | | 135 | |
| VABM-L-14...G14-7 | | | | |

| Type | B1 | B2 | B3 | B4 | L1 | L2 | L3 |
|--------------------|------|----|------|-----|-------|----|------|
| VABM-L-14...G14-8 | 59.3 | 1 | 49.3 | 8.3 | 167.9 | 56 | 43.4 |
| VABM-L-14...G14-9 | | | | | 183.9 | | |
| VABM-L-14...G14-10 | | | | | 199.9 | | |
| VABM-L-14...G14-12 | | | | | 231.9 | | |
| VABM-L-14...G14-16 | | | | | 295.9 | | |
| VABM-L-14...G14-20 | | | | | 359.9 | | |
| VABM-L-14...G14-24 | | | | | 423.9 | | |

Dimensions – Mounting holes, size 10

Download CAD data → www.festo.com




| Type | | B1 | B2 | L1 | L2 | L3 | L4 | I-Port interface, outlet on the side L4 |
|----------------------|-----------------|------|----|-------|-----|-------|----|-----------------------------------------|
| VABM-L1-10...-G18-4 | Up to 8 valves | 52.2 | 5 | 82 | - | - | 13 | 62.5 |
| VABM-L1-10...-G18-5 | | | | 92.5 | - | - | | |
| VABM-L1-10...-G18-6 | | | | 103 | - | - | | |
| VABM-L1-10...-G18-7 | | | | 113.5 | - | - | | |
| VABM-L1-10...-G18-8 | Up to 20 valves | 52.2 | 5 | 124 | - | - | 13 | 62.5 |
| VABM-L1-10...-G18-9 | | | | 134.5 | - | 67.25 | | |
| VABM-L1-10...-G18-10 | | | | 145 | - | 72.5 | | |
| VABM-L1-10...-G18-12 | | | | 166 | - | 83 | | |
| VABM-L1-10...-G18-16 | | | | 208 | - | 104 | | |
| VABM-L1-10...-G18-20 | | | | 250 | - | 125 | | |
| VABM-L1-10...-G18-24 | 24 valves | 52.2 | 5 | 292 | 192 | 100 | 13 | 62.5 |

Valve terminals VTUG with multi-pin plug and fieldbus connection

Dimensions

Dimensions – Mounting holes, size 14

Download CAD data → www.festo.com



| Type | | B1 | B2 | L1 | L2 | L3 | L4 | L5 | I-Port interface, outlet on the side L4 |
|----------------------|-------------------------|------|----|-----|-----|-----|-----|----|-----------------------------------------|
| VABM-L1-14...-G14-4 | Up to 8 valves | 59.3 | 6 | 116 | – | – | – | 6 | 55.5 |
| VABM-L1-14...-G14-5 | | | | 132 | – | – | – | | |
| VABM-L1-14...-G14-6 | | | | 148 | – | – | – | | |
| VABM-L1-14...-G14-7 | | | | 164 | – | – | – | | |
| VABM-L1-14...-G14-8 | 8 to 10 valves | | | 180 | – | – | 90 | | |
| VABM-L1-14...-G14-9 | | | | 196 | – | – | 98 | | |
| VABM-L1-14...-G14-10 | | | | 212 | – | – | 106 | | |
| VABM-L1-14...-G14-12 | 12 valves and 16 valves | | | 244 | – | 162 | 82 | | |
| VABM-L1-14...-G14-16 | | | | 308 | – | 204 | 104 | | |
| VABM-L1-14...-G14-20 | 20 valves and 24 valves | | | 372 | 279 | 186 | 93 | | |
| VABM-L1-14...-G14-24 | | | | 436 | 327 | 218 | 109 | | |

Valve terminals VTUG with multi-pin plug and fieldbus connection

Order code – Manifold rail

| | | | | | | | |
|-----------------------------|---|-----------|--|--|--|-----------|------------|
| VABM | - | | | | | | |
| Designation | | | | | | | |
| Manifold rail | | L1 | | | | | |
| Size | | | | | | | |
| Size 10 | | | | | | 10 | |
| Size 14 | | | | | | 14 | |
| Version | | | | | | | |
| Standard | | | | | | | - |
| High flow rate | | | | | | | H |
| Connection type | | | | | | | |
| Semi in-line | | | | | | | G |
| Sub-base | | | | | | | W |
| Connection direction | | | | | | | |
| Side | | | | | | | - |
| Underneath | | | | | | | B |
| Pneumatic connection | | | | | | | |
| G1/8 | | | | | | | G18 |
| G1/4 | | | | | | | G14 |

| | | | | | | | |
|--------------------------------------------------|--|--|--|--|--|--|------------------------------------------------------------|
| | | | | | | | |
| Outlet direction of electrical components | | | | | | | |
| | | | | | | | - Top |
| Circuitry | | | | | | | |
| | | | | | | | - None |
| | | | | | | | R Holding current reduction with protective circuit |
| Electrical connection | | | | | | | |
| | | | | | | | - None |
| | | | | | | | G Preparation for electrical connection |
| Connection for valve function | | | | | | | |
| | | | | | | | - 5/2-way |
| | | | | | | | M 5/2-way, single solenoid |
| Valve positions | | | | | | | |
| 4 | | | | | | | 4 valve positions |
| 5 | | | | | | | 5 valve positions |
| 6 | | | | | | | 6 valve positions |
| 7 | | | | | | | 7 valve positions |
| 8 | | | | | | | 8 valve positions |
| 9 | | | | | | | 9 valve positions |
| 10 | | | | | | | 10 valve positions |
| 12 | | | | | | | 12 valve positions |
| 16 | | | | | | | 16 valve positions |
| 20 | | | | | | | 20 valve positions |
| 24 | | | | | | | 24 valve positions |

Valve terminals VTUG with multi-pin plug connection

Technical data – Multi-pin plug connection

The following multi-pin plug connections are available for the valve terminal VTUG:

- Sub-D (25-pin)
- Sub-D (44-pin)
- Flat cable (26-pin)
- Flat cable (50-pin)



Electrical multi-pin plug

Each pin on the multi-pin plug can actuate exactly one solenoid coil.

If the maximum configurable number of valve positions is 24, this means that 48 valve functions can be addressed.

The valves can be switched by means of positive or negative logic (positive switching or negative switching).

Mixed operation is generally not possible, however an exception is made for certain variants (V22 ... 25) with 25-pin Sub-D. In this case, a specific range of valve positions (e.g. Com 16...19) is supplied with

common voltage. This allows these ranges to be switched with positive or negative logic and valve groups to be switched off independently of the other ranges. Mixed operation within a range is not permitted.




A double solenoid valve occupies one valve position and two pins on the multi-pin plug. This means that the number of double solenoid valves per manifold rail is limited (→ pin allocation page 110)

| General technical data | | | | |
|--------------------------------|-----------------|-----------------|-----------------|-----------------|
| Type | VAEM-L1-S-M1-25 | VAEM-L1-S-M1-44 | VAEM-L1-S-M3-26 | VAEM-L1-S-M3-50 |
| Number of pins | 25-pin | 44-pin | 26-pin | 50-pin |
| Electrical connection | Sub-D plug | | Flat cable plug | |
| Max. number of valve positions | 24 | | 24 | |
| Protection class to EN 60529 | IP67 | | IP40 | |
| Material | Polyamide | | Polyamide | |
| Note on materials | RoHS-compliant | | RoHS-compliant | |
| Weight | 53 | | 45 | 48 |

Valve terminals VTUG with multi-pin plug connection

Technical data – Multi-pin plug connection

| Pin allocation – Sub-D plug, 25-pin | | | | | | | | | |
|-----------------------------------------------------------------------------------|-------------|---------------------|----|------------------------------------------|----|-------------------------------------------|-----|---------------------|----|
| | M1-25 (V20) | | | | | | | | |
| | Pin | 12x double solenoid | | 8x double solenoid 8x single solenoid | | 4x double solenoid 16x single solenoid | | 24x single solenoid | |
|  | 1 | VP0 | 14 | VP0 | 14 | VP0 | 14 | VP0 | 14 |
| | 2 | VP0 | 12 | VP0 | 12 | VP0 | 12 | VP23 | 14 |
| | 3 | VP1 | 14 | VP1 | 14 | VP1 | 14 | VP1 | 14 |
| | 4 | VP1 | 12 | VP1 | 12 | VP1 | 12 | VP22 | 14 |
| | 5 | VP2 | 14 | VP2 | 14 | VP2 | 14 | VP2 | 14 |
| | 6 | VP2 | 12 | VP2 | 12 | VP2 | 12 | VP21 | 14 |
| | 7 | VP3 | 14 | VP3 | 14 | VP3 | 14 | VP3 | 14 |
| | 8 | VP3 | 12 | VP3 | 12 | VP3 | 12 | VP20 | 14 |
| | 9 | VP4 | 14 | VP4 | 14 | VP4 | 14 | VP4 | 14 |
| | 10 | VP4 | 12 | VP4 | 12 | VP19 | 14 | VP19 | 14 |
| | 11 | VP5 | 14 | VP5 | 14 | VP5 | 14 | VP5 | 14 |
| | 12 | VP5 | 12 | VP5 | 12 | VP18 | 14 | VP18 | 14 |
| | 13 | VP6 | 14 | VP6 | 14 | VP6 | 14 | VP6 | 14 |
| | 14 | VP6 | 12 | VP6 | 12 | VP17 | 14 | VP17 | 14 |
| | 15 | VP7 | 14 | VP7 | 14 | VP7 | 14 | VP7 | 14 |
| | 16 | VP7 | 12 | VP7 | 12 | VP16 | 14 | VP16 | 14 |
| | 17 | VP8 | 14 | VP8 | 14 | VP8 | 14 | VP8 | 14 |
| | 18 | VP8 | 12 | VP15 | 14 | VP15 | 14 | VP15 | 14 |
| | 19 | VP9 | 14 | VP9 | 14 | VP9 | 14 | VP9 | 14 |
| | 20 | VP9 | 12 | VP14 | 14 | VP14 | 14 | VP14 | 14 |
| | 21 | VP10 | 14 | VP10 | 14 | VP10 | 14 | VP10 | 14 |
| | 22 | VP10 | 12 | VP13 | 14 | VP13 | 14 | VP13 | 14 |
| | 23 | VP11 | 14 | VP11 | 14 | VP11 | 14 | VP11 | 14 |
| | 24 | VP11 | 12 | VP12 | 14 | VP12 | 14 | VP12 | 14 |
| | 25 | Com | | Com | | Com | Com | Com | |

 - Note



A grey field means that a double solenoid valve can be used, while a white field means that only single solenoid valves can be used.

VP Valve position

Valve terminals VTUG with multi-pin plug connection

Technical data – Multi-pin plug connection

| Pin allocation – Sub-D plug, 25-pin | | | | | | | | | | Pin allocation – Sub-D plug, 44-pin | | | |
|-------------------------------------|---------------|----|---------------|----|---------------|----|---------------|----|-----|-------------------------------------|-----------------------------------------|--|--|
| Pin | M1-25V1 (V22) | | M1-25V2 (V23) | | M1-25V3 (V24) | | M1-25V4 (V25) | | Pin | M1-44 (V21) | | | |
| | | | | | | | | | | | 18x double solenoid, 6x single solenoid | | |
| 1 | VP0 | 14 | VP0 | 14 | VP0 | 14 | VP0 | 14 | 1 | VP0 | 14 | | |
| 2 | VP0 | 12 | VP0 | 12 | VP0 | 12 | VP1 | 14 | 2 | VP0 | 12 | | |
| 3 | VP1 | 14 | VP1 | 14 | VP1 | 14 | VP2 | 14 | 3 | VP1 | 14 | | |
| 4 | VP1 | 12 | VP1 | 12 | VP1 | 12 | VP3 | 14 | 4 | VP1 | 12 | | |
| 5 | VP2 | 14 | VP2 | 14 | VP2 | 14 | VP4 | 14 | 5 | VP2 | 14 | | |
| 6 | VP2 | 12 | VP2 | 12 | VP2 | 12 | VP5 | 14 | 6 | VP2 | 12 | | |
| 7 | VP3 | 14 | VP3 | 14 | VP3 | 14 | VP6 | 14 | 7 | VP3 | 14 | | |
| 8 | VP3 | 12 | VP3 | 12 | VP3 | 12 | VP7 | 14 | 8 | VP3 | 12 | | |
| 9 | VP4 | 14 | VP4 | 14 | VP4 | 14 | VP8 | 14 | 9 | VP4 | 14 | | |
| 10 | VP4 | 12 | VP4 | 12 | VP5 | 14 | VP9 | 14 | 10 | VP4 | 12 | | |
| 11 | VP5 | 14 | VP5 | 14 | VP6 | 14 | VP10 | 14 | 11 | VP5 | 14 | | |
| 12 | VP5 | 12 | VP5 | 12 | VP7 | 14 | VP11 | 14 | 12 | VP5 | 12 | | |
| 13 | VP6 | 14 | VP6 | 14 | VP8 | 14 | VP12 | 14 | 13 | VP6 | 14 | | |
| 14 | VP6 | 12 | VP6 | 12 | VP9 | 14 | VP13 | 14 | 14 | VP6 | 12 | | |
| 15 | VP7 | 14 | VP7 | 14 | VP10 | 14 | VP14 | 14 | 15 | VP7 | 14 | | |
| 16 | VP7 | 12 | VP7 | 12 | VP11 | 14 | VP15 | 14 | 16 | VP7 | 12 | | |
| 17 | VP8 | 14 | VP8 | 14 | VP12 | 14 | VP16 | 14 | 17 | VP8 | 14 | | |
| 18 | VP8 | 12 | VP9 | 14 | VP13 | 14 | VP17 | 14 | 18 | VP8 | 12 | | |
| 19 | VP9 | 14 | VP10 | 14 | VP14 | 14 | VP18 | 14 | 19 | VP9 | 14 | | |
| 20 | VP9 | 12 | VP11 | 14 | VP15 | 14 | VP19 | 14 | 20 | VP9 | 12 | | |
| 21 | Com 16 ... 19 | | 21 | VP10 | 14 | | |
| 22 | Com 12 ... 15 | | 22 | VP10 | 12 | | |
| 23 | Com 8 ... 11 | | 23 | VP11 | 14 | | |
| 24 | Com 4 ... 7 | | 24 | VP11 | 12 | | |
| 25 | Com 0 ... 3 | | 25 | VP12 | 14 | | |
| - | | | | | | | | | 26 | VP12 | 12 | | |
| - | | | | | | | | | 27 | VP13 | 14 | | |
| - | | | | | | | | | 28 | VP13 | 12 | | |
| - | | | | | | | | | 29 | VP14 | 14 | | |
| - | | | | | | | | | 30 | VP14 | 12 | | |
| - | | | | | | | | | 31 | VP15 | 14 | | |
| - | | | | | | | | | 32 | VP15 | 12 | | |
| - | | | | | | | | | 33 | VP16 | 14 | | |
| - | | | | | | | | | 34 | VP16 | 12 | | |
| - | | | | | | | | | 35 | VP17 | 14 | | |
| - | | | | | | | | | 36 | VP17 | 12 | | |
| - | | | | | | | | | 37 | VP18 | 14 | | |
| - | | | | | | | | | 38 | VP19 | 14 | | |
| - | | | | | | | | | 39 | VP20 | 14 | | |
| - | | | | | | | | | 40 | VP21 | 14 | | |
| - | | | | | | | | | 41 | VP22 | 14 | | |
| - | | | | | | | | | 42 | VP23 | 14 | | |
| - | | | | | | | | | 43 | com | | | |
| - | | | | | | | | | 44 | | | | |





 Note
A grey field means that a double solenoid valve can be used, while a white field means that only single solenoid valves can be used.

VP Valve position

Valve terminals VTUG with multi-pin plug connection

Technical data – Multi-pin plug connection

| Pin allocation – Flat cable, 26-pin | | | | | | | | | | Pin allocation – Flat cable, 50-pin | | | |
|-------------------------------------|---------------------|----|------------------------------------------|----|-------------------------------------------|-----|---------------------|----|-----|-------------------------------------|----|--|--|
| M3-26 (V20) | | | | | | | | | | M3-50 (V26) | | | |
| Pin | 12x double solenoid | | 8x double solenoid 8x single solenoid | | 4x double solenoid 16x single solenoid | | 24x single solenoid | | Pin | | | | |
| 1 | VP0 | 14 | VP0 | 14 | VP0 | 14 | VP0 | 14 | 1 | VP0 | 14 | | |
| 2 | VP0 | 12 | VP0 | 12 | VP0 | 12 | VP23 | 14 | 2 | VP0 | 12 | | |
| 3 | VP1 | 14 | VP1 | 14 | VP1 | 14 | VP1 | 14 | 3 | VP1 | 14 | | |
| 4 | VP1 | 12 | VP1 | 12 | VP1 | 12 | VP22 | 14 | 4 | VP1 | 12 | | |
| 5 | VP2 | 14 | VP2 | 14 | VP2 | 14 | VP2 | 14 | 5 | VP2 | 14 | | |
| 6 | VP2 | 12 | VP2 | 12 | VP2 | 12 | VP21 | 14 | 6 | VP2 | 12 | | |
| 7 | VP3 | 14 | VP3 | 14 | VP3 | 14 | VP3 | 14 | 7 | VP3 | 14 | | |
| 8 | VP3 | 12 | VP3 | 12 | VP3 | 12 | VP20 | 14 | 8 | VP3 | 12 | | |
| 9 | VP4 | 14 | VP4 | 14 | VP4 | 14 | VP4 | 14 | 9 | VP4 | 14 | | |
| 10 | VP4 | 12 | VP4 | 12 | VP19 | 14 | VP19 | 14 | 10 | VP4 | 12 | | |
| 11 | VP5 | 14 | VP5 | 14 | VP5 | 14 | VP5 | 14 | 11 | VP5 | 14 | | |
| 12 | VP5 | 12 | VP5 | 12 | VP18 | 14 | VP18 | 14 | 12 | VP5 | 12 | | |
| 13 | VP6 | 14 | VP6 | 14 | VP6 | 14 | VP6 | 14 | 13 | VP6 | 14 | | |
| 14 | VP6 | 12 | VP6 | 12 | VP17 | 14 | VP17 | 14 | 14 | VP6 | 12 | | |
| 15 | VP7 | 14 | VP7 | 14 | VP7 | 14 | VP7 | 14 | 15 | VP7 | 14 | | |
| 16 | VP7 | 12 | VP7 | 12 | VP16 | 14 | VP16 | 14 | 16 | VP7 | 12 | | |
| 17 | VP8 | 14 | VP8 | 14 | VP8 | 14 | VP8 | 14 | 17 | VP8 | 14 | | |
| 18 | VP8 | 12 | VP15 | 14 | VP15 | 14 | VP15 | 14 | 18 | VP8 | 12 | | |
| 19 | VP9 | 14 | VP9 | 14 | VP9 | 14 | VP9 | 14 | 19 | VP9 | 14 | | |
| 20 | VP9 | 12 | VP14 | 14 | VP14 | 14 | VP14 | 14 | 20 | VP9 | 12 | | |
| 21 | VP10 | 14 | VP10 | 14 | VP10 | 14 | VP10 | 14 | 21 | VP10 | 14 | | |
| 22 | VP10 | 12 | VP13 | 14 | VP13 | 14 | VP13 | 14 | 22 | VP10 | 12 | | |
| 23 | VP11 | 14 | VP11 | 14 | VP11 | 14 | VP11 | 14 | 23 | VP11 | 14 | | |
| 24 | VP11 | 12 | VP12 | 14 | VP12 | 14 | VP12 | 14 | 24 | VP11 | 12 | | |
| 25 | Com | | Com | | Com | Com | Com | | 25 | VP12 | 14 | | |
| 26 | Com | | Com | | Com | | Com | | 26 | VP12 | 12 | | |
| - | | | | | | | | | 27 | VP13 | 14 | | |
| - | | | | | | | | | 28 | VP13 | 12 | | |
| - | | | | | | | | | 29 | VP14 | 14 | | |
| - | | | | | | | | | 30 | VP14 | 12 | | |
| - | | | | | | | | | 31 | VP15 | 14 | | |
| - | | | | | | | | | 32 | VP15 | 12 | | |
| - | | | | | | | | | 33 | VP16 | 14 | | |
| - | | | | | | | | | 34 | VP16 | 12 | | |
| - | | | | | | | | | 35 | VP17 | 14 | | |
| - | | | | | | | | | 36 | VP17 | 12 | | |
| - | | | | | | | | | 37 | VP18 | 14 | | |
| - | | | | | | | | | 38 | VP18 | 12 | | |
| - | | | | | | | | | 39 | VP19 | 14 | | |
| - | | | | | | | | | 40 | VP19 | 12 | | |
| - | | | | | | | | | 41 | VP20 | 14 | | |
| - | | | | | | | | | 42 | VP20 | 12 | | |
| - | | | | | | | | | 43 | VP21 | 14 | | |
| - | | | | | | | | | 44 | VP21 | 12 | | |
| - | | | | | | | | | 45 | VP22 | 14 | | |
| - | | | | | | | | | 46 | VP22 | 12 | | |
| - | | | | | | | | | 47 | VP23 | 14 | | |
| - | | | | | | | | | 48 | VP23 | 12 | | |
| - | | | | | | | | | 49 | Com | | | |
| - | | | | | | | | | 50 | | | | |



Note
A grey field means that a double solenoid valve can be used, while a white field means that only single solenoid valves can be used.


Valve terminals VTUG with multi-pin plug connection

Technical data – Multi-pin plug connection

Dimensions

Download CAD data → www.festo.com

Multi-pin plug connection, Sub-D




 - Note
Dimensions of the manifold
rail with electrical connection
(→ 99)

| Type | B1 | L1 | H1 |
|------------------|------|------|------|
| VAEM-L1-S-M3-... | 90.5 | 41.9 | 18.9 |

Dimensions

Download CAD data → www.festo.com

Multi-pin plug connection, flat cable plug






 - Note
Dimensions of the manifold
rail with electrical connection
(→ 99)

| Type | B1 | L1 | H1 |
|------------------|------|------|------|
| VAEM-L1-S-M3-... | 90.5 | 41.9 | 32.7 |

Valve terminals VTUG with multi-pin plug connection

Accessories – Multi-pin plug connection

| Ordering data – Multi-pin plug connection | | | |
|-----------------------------------------------------------------------------------------------------------------------------|-------------------------------------------------|---------------------------|-----------------------------------|
| | Description | | Type |
| Electrical interface, Sub-D | | | |
|  | 25-pin | For variant M1-25 (V20) | VAEM-L1-S-M1-25 |
| | | For variant M1-25V1 (V22) | VAEM-L1-S-M1-25V1 |
| | | For variant M1-25V2 (V23) | VAEM-L1-S-M1-25V2 |
| | | For variant M1-25V3 (V24) | VAEM-L1-S-M1-25V3 |
| | | For variant M1-25V4 (V25) | VAEM-L1-S-M1-25V4 |
| | 44-pin | For variant M1-44 (V21) | VAEM-L1-S-M1-44 |
| Electrical interface, flat cable plug | | | |
|  | 26-pin | For variant M3-26 (V20) | VAEM-L1-S-M3-26 |
| | 50-pin | For variant M3-50 (V26) | VAEM-L1-S-M3-50 |
| Connecting cable for multi-pin plug, 25-pin, IP40 Technical data → Internet: kmp | | | |
|  | Sub-D, 25-wire, straight socket, up to 24 coils | 2.5 | KMP6-25P-20-2,5 |
| | | 5 | KMP6-25P-20-5 |
| | | 10 | KMP6-25P-20-10 |
| Connecting cable for multi-pin plug, 25-pin, IP67 Technical data → Internet: nebv | | | |
|  | Sub-D, 25-wire, straight socket, up to 24 coils | 2.5 | NEBV-S1G25-K-2.5-N-LE25 |
| | | 5 | NEBV-S1G25-K-5-N-LE25 |
| | | 10 | NEBV-S1G25-K-10-N-LE25 |
| Connecting cable for multi-pin plug, 44-pin, IP40 Technical data → Internet: nebv | | | |
|  | Sub-D, 44-wire, straight socket, up to 35 coils | 2.5 | NEBV-S1G44-K-2.5-N-LE44-S6 |
| | | 5 | NEBV-S1G44-K-5-N-LE44-S6 |
| | | 10 | NEBV-S1G44-K-10-N-LE44-S6 |

Valve terminals VTUG, IO-Link interface

Technical data – IO-Link interface

Festo-specific, standardised interface for direct connection to the fieldbus via the bus node CTEU or to an IO-Link master via a cable (in IO-Link mode).



I-Port interface/IO-Link

Versions:

- I-Port interface for fieldbus nodes (CTEU)
- IO-Link mode for direct connection to a higher-level IO-Link master

The following protocols are supported in connection with the associated CTEU node:

- CANopen
- DeviceNet
- PROFIBUS
- CC-LINK
- EtherCAT

The electrical supply/transmission of communication data takes place via an M12 plug.

The valve terminal can be equipped with 4 ... 24 (double solenoid) valves.


General technical data

| | | | |
|------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------|--------|------------|
| Communication types | IO-Link | | |
| Electrical connection | <ul style="list-style-type: none"> • M12 plug, 5-pin • A-coded • Metal thread for screening | | |
| Baud rates | COM3 | [kbps] | 230.4 |
| | COM2 | [kbps] | 38.4 |
| Intrinsic current consumption, logic supply PS | | [mA] | 30 |
| Intrinsic current consumption, valve supply PL | | [mA] | 30 |
| Max. number of solenoid coils | VAEM-L1-S-8-PT | | 16 |
| | VAEM-L1-S-16-PT | | 32 |
| | VAEM-L1-S-24-PT | | 48 |
| Max. number of valve positions | VAEM-L1-S-8-PT | | 8 |
| | VAEM-L1-S-16-PT | | 16 |
| | VAEM-L1-S-24-PT | | 24 |
| Ambient temperature | | [°C] | -5 ... +50 |
| Protection class to EN 60529 | IP67 | | |

LED display

| | Colour | Status | Function |
|---------------|-----------|--------------------|---------------------------------------------------------|
| Status LED X1 | Red/green | Off | No 24 V logic |
| | | Static green | Everything OK |
| | | Flashing green | Communication error (in the I-Port or IO-Link protocol) |
| | | Flashing red/green | Load supply error (undervoltage or no load supply) |
| | | Static red | Load supply error and communication error |


Pin allocation – I-Port interface/IO-Link

| | Pin | Designation corresponds to IO-Link |
|-------------------------------------------------------------------------------------|-----|------------------------------------|
|  | 1 | Supply PS (+24 V) |
| | 2 | Load supply PL (+24 V) |
| | 3 | Supply PS (0 V) |
| | 4 | Communication signal C/Q |
| | 5 | Load supply PL (0V) |

Valve terminals VTUG, IO-Link interface

Technical data – I-Port interface/IO-Link

System overview – IO-Link



- Communication with the higher-order controller via fieldbus
- Use a fieldbus node CTEU compatible with the fieldbus protocol
- Up to 64 inputs/outputs (solenoid coils), depending on the valve terminal
- No preprocessing


Valve terminals VTUG, IO-Link interface

Technical data – I-Port interface/IO-Link

Dimensions

Download CAD data → www.festo.com

I-Port interface, outlet on top




 Note
Dimensions of the manifold rail with electrical connection (→ 99)

Dimensions

Download CAD data → www.festo.com

I-Port interface, outlet on the side



 Note
Dimensions of the manifold rail with electrical connection (→ 99)

| Type | Outlet on top | | | Outlet on the side | | |
|---------------|---------------|------|----|--------------------|------|----|
| | B1 | L1 | H1 | B1 | L1 | L2 |
| VAEM-L1-S-... | 91 | 42.5 | 25 | 91.5 | 47.1 | 10 |

Ordering data – I-Port interface/IO-Link

| | Description | Type |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|------------------|
| Electrical interface for I-Port interface/IO-Link, outlet on top | | |
|  | Actuation of up to 8 double solenoid valve positions | VAEM-L1-S-8-PT |
| | Actuation of up to 16 double solenoid valve positions | VAEM-L1-S-16-PT |
| | Actuation of up to 24 double solenoid valve positions | VAEM-L1-S-24-PT |
| Electrical interface for I-Port interface/IO-Link, outlet on the side | | |
|  | Actuation of up to 8 double solenoid valve positions | VAEM-L1-S-8-PTL |
| | Actuation of up to 16 double solenoid valve positions | VAEM-L1-S-16-PTL |
| | Actuation of up to 24 double solenoid valve positions | VAEM-L1-S-24-PTL |
| Connection technology for IO-Link | | |
|  | T-adapter M12, 5-pin for IO-Link and load supply | FB-TA-M12-5POL |
| Straight plug, for I-Port interface/IO-Link | | |
|  | Straight plug, M12, 5-pin (in combination with adapter for separate load supply) | SEA-M12-5GS-PG7 |
| Inscription label for I-Port interface/IO-Link | | |
|  | 40 pieces in frame | ASLR-C-E4 |

Valve terminals VTUG, decentralised adapter CAPC

Technical data – CAPC

Function

The E-box CAPC enables the decentralised installation of fieldbus nodes CTEU on a valve terminal or input modules with I-Port interface.

Application

- M12 connection technology (two interfaces)
- Enables the installation of valve terminals or other devices over a distance of 20 metres
- Accessory CAFM enables the E-box to be installed on an H-rail



| General technical data | | |
|---------------------------|---------------|-----------------------|
| Type | CAPC-F1-E-M12 | |
| Dimensions W x L x H | [mm] | 50 x 148 x 28 |
| Fieldbus interface | | 2 x M12 socket, 5-pin |
| Operating voltage range | [V DC] | 18 ... 30 |
| Max. power supply | [A] | 2 |
| Nominal operating voltage | [V DC] | 24 |
| Product weight | [g] | 85 |
| Cable length | [m] | 20 |

| Materials | |
|-------------------|----------------|
| Housing | PA reinforced |
| Note on materials | RoHS-compliant |

| Operating and environmental conditions | |
|----------------------------------------------|-----------------------------------|
| Protection class to EN 60529 | IP65, IP67 |
| Ambient temperature | [°C] -5 ... +50 |
| Storage temperature | [°C] -20 ... +70 |
| Corrosion resistance class CRC ¹⁾ | 2 ¹⁾ |
| CE marking (see declaration of conformity) | To EU EMC Directive ²⁾ |

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 2) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com → Support → User documentation.
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

| Pin allocation – Power supply/IO-Link interfaces | | | |
|--------------------------------------------------|-----|--------------------------|-------------------------------|
| | Pin | Designation | Function |
| | 1 | Supply PS (+24 V) | Power supply for system +24 V |
| | 2 | Load supply PL (+24 V) | Power supply for load +24 V |
| | 3 | Supply PS (0 V) | Power supply for system +24 V |
| | 4 | Communication signal C/Q | Communication signal C/Q |
| | 5 | Load supply PL (0V) | Power supply for load 0 V |
| | | | Metal thread for FE |


Valve terminals VTUG, decentralised adapter CAPC

Technical data – CAPC


Dimensions

Download CAD data → www.festo.com

CAPC




CAPC with mounted fieldbus node CTEU-CO







| Type | B1 | B2 | B3 | B4 | B5 | D1-∅ | H1 | H2 | H3 | H4 | H5 | H6 | L1 | L2 |
|------|-----|-----|----|-----|----|------|------|------|------|-----|-----|------|----|----|
| CAPC | 148 | 140 | 32 | 6.6 | 91 | 4.4 | 27.3 | 20.3 | 19.3 | 9.6 | 5.7 | 54.8 | 50 | 40 |

Accessory CAPC

| Ordering data | | Part No. | Type |
|-------------------------------------------------------------------------------------|---|----------|---------------|
| E-box | | | |
|  | - | 570042 | CAPC-F1-E-M12 |
| H-rail mounting | | | |
|  | - | 570043 | CAF-M-F1-H |

Valve terminals VTUG with multi-pin plug and fieldbus connection

Accessories – Valve terminal

| Ordering data – CTEU | | |
|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|-----------------------|
| | Description | Type |
| Bus node | | |
|  | CANopen bus node | CTEU-CO |
| | CC-Link bus node | CTEU-CC |
| | PROFIBUS bus node | CTEU-PB |
| | DeviceNet bus node | CTEU-DN |
|  | EtherCAT bus node | CTEU-EC |
| Bus connection | | |
|  | Sub-D plug, straight, for CANopen | FBS-SUB-9-BU-2x5POL-B |
| | Sub-D plug, straight, for CC-Link | FBS-SUB-9-GS-2x4POL-B |
| | Sub-D plug, straight, for PROFIBUS | FFBS-SUB-9-GS-DP-B |
|  | Sub-D plug, angled, for CANopen, 9-pin | FBS-SUB-9-WS-CO-K |
| | Sub-D plug, angled, for PROFIBUS, 9-pin | FBS-SUB-9-WS-PB-K |
|  | M12x1, 5-pin, A-coded, for CANopen | FBA-2-M12-5POL |
| | M12x1, 5-pin, B-coded, for PROFIBUS | FBA-2-M12-5POL-RK |
|  | For 5-pin terminal strip for CANopen | FBA-1-SL-5POL |
|  | Terminal strip, 5-pin, for DeviceNet/CANopen | FBSD-KL-2x5POL |
|  | Screw terminal for CC-Link | FBA-1-KL-5POL |
|  | Fieldbus socket, M12x1, 5-pin, for CANopen | FBSD-GD-9-5POL |
| | Plug, M12x1, 5-pin, for CANopen | FBS-M12-5GS-PG9 |
|  | Straight socket, M12x1, 5-pin, for assembling a connecting cable compatible with FBA-2-M12-5POL-RK for PROFIBUS | NECU-M-B12G5-C2-PB |
|  | Straight plug, M12x1, 5-pin, for assembling a connecting cable compatible with FBA-2-M12-5POL-RK for PROFIBUS | NECU-M-S-B12G5-C2-PB |
|  | Terminating resistor, M12, B-coded for PROFIBUS | CACR-S-B12G5-220-PB |
|  | Plug M12x1, 4-pin, D-coded for EtherCAT | NECU-M-S-D12G4-C2-ET |

Valve terminals VTUG with multi-pin plug and fieldbus connection


Accessories – Valve terminal

| Ordering data – CTEU | | |
|-----------------------------------------------------------------------------------|----------------------------------------------------------------|-----------------------|
| | Description | Type |
| Plug socket | | |
|  | For power supply, M12x1, 5-pin, B-coded for CANopen/DeviceNet | NTSD-GD-9-M12-5POL-RK |
| | For power supply, M12x1, 5-pin for CC-Link, PROFIBUS, EtherCAT | FBSD-GD-9-5POL |
| Inscription label | | |
|  | For bus node | ASLR-C-E4 |

| Ordering data | | |
|--------------------------------------------------------------------------------------|------------------------------------------|--------------------|
| | Description | Type |
| Silencer Technical data → Internet: u | | |
|  | For thread M5 | U-M5 UC-M5 |
| | For thread M7 | UC-M7 |
| | For thread G ¹ / ₈ | U-1/8-50 UC-1/8 |
| | For thread G ¹ / ₄ | U-1/4-20 |
| | | UC-1/4-20 |
| Fittings Technical data → Internet: qs | | |
|  | For tubing Ø 3 mm | QSM-M5-3-I-R-100 |
| | For tubing Ø 4 mm | QSM-M5-4-I-R-100 |
| | For tubing Ø 4 mm | QSM-M5-4-I-R-100 |
| | For tubing Ø 6 mm | QSM-M7-6-I-R-100 |
| | For tubing Ø 3 mm | QSM-M5-3-I |
| | For tubing Ø 4 mm | QSM-M5-4-I |
| | For tubing Ø 4 mm | QSM-M7-4-I |
| | For tubing Ø 4 mm | QS-G1/8-4-I |
| | For tubing Ø 6 mm | QS-G1/8-6-I |
| | For tubing Ø 8 mm | QS-G1/8-8-I |
| | For tubing Ø 8 mm | QS-B-1/4-8-I-20 |
| | For tubing Ø 10 mm | QS-B-1/4-10-I-20 |
| | For tubing Ø 12 mm | QS-B-1/4-12-I-20 |
| | For tubing Ø 10 mm | QS-B-1/8-10-I-20 |
| | For tubing Ø 6 mm | QSL-G1/8-6 |
| | For tubing Ø 8 mm | QSL-G1/8-8 |
| | For tubing Ø 12 mm | QSL-B-1/4-8-20 |
| | For tubing Ø 10 mm | QSL-B-1/4-10-20 |
| | For tubing Ø 12 mm | QSL-B-1/4-12-20 |
| | For tubing Ø 10 mm | QSL-B-1/8-10-20 |
| | For tubing Ø 6 mm | QSL-G1/8-6 |
| | For tubing Ø 8 mm | QSL-G1/8-8 |
| | For tubing Ø 6 mm | QSM-L-G1/8-6-20 |
| | For tubing Ø 3 mm | QSM-L-M5-3 |
| | For tubing Ø 4 mm | QSM-L-M5-4 |
| For tubing Ø 4 mm | QSM-L-M7-4 | |
| For tubing Ø 3 mm | QSM-L-L-M5-3 | |
| For tubing Ø 4 mm | QSM-L-L-M5-4 | |
| For tubing Ø 4 mm | QSM-L-L-M7-4 | |
| Blanking plug Technical data → Internet: b | | |
|  | For thread M5 | B-M5-B |
| | For thread M7 | B-M7 |
| | For thread G ¹ / ₈ | B-1/8 |
| | For thread G ¹ / ₄ | B-1/4 |

Valve terminals VTUG with multi-pin plug and fieldbus connection

Accessories – Valve terminal

| Ordering data | | | |
|---------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------|-----------|------------------------|
| | Description | | Type |
| Blanking plate | | | |
|  | Vacant position 10 mm | | VABB-L1-10-T |
| | Vacant position 14 mm | | VABB-L1-14-T |
| Supply plate | | | |
|  | Supply ports 1, 3, 5 10 mm | | VABF-L1-10-P3A4-M7-T1 |
| | Supply ports 1, 3, 5 14 mm | | VABF-L1-14-P3A4-G18-T1 |
| Separator | | | |
|  | Separator for sub-base manifold rail 10 | | VABD-6-B |
| | Separator for semi in-line manifold rail 10 | | VABD-8-B |
| | Separator for all manifold rails 14 | | VABD-10-B |
| H-rail Technical data → Internet: nrh | | | |
|  | To EN 60715, 35 x 7.5 (WxH) | 2 m | NRH-35-2000 |
| H-rail mounting Technical data → Internet: vame | | | |
|  | Use the following screws for mounting: Size 10: DIN 912 M4x30 Size 14: DIN 912 M4x40 | 2 pieces | VAME-T-M4 |
| Cover cap for manual override Technical data → Internet: vmpa | | | |
|  | Covered | 10 pieces | VMPA-HBV-B |
|  | Non-detenting | | VMPA-HBT-B |

Valve terminals VTUG with multi-pin plug and fieldbus connection

Accessories – Valve terminal

| Ordering data | | |
|-----------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------|
| | Description | Type |
| Inscription label holder | | Technical data → Internet: aslr |
|  | Holder for an inscription label and covering the mounting screw and manual override | 10 pieces ASLR-D-L1 |
| Inscription label holder for valve terminal | | |
|  | For 4 valve positions, size 10 | ASCF-H-L1-10-4V |
| | For 5 valve positions, size 10 | ASCF-H-L1-10-5V |
| | For 6 valve positions, size 10 | ASCF-H-L1-10-6V |
| | For 7 valve positions, size 10 | ASCF-H-L1-10-7V |
| | For 8 valve positions, size 10 | ASCF-H-L1-10-8V |
| | For 9 valve positions, size 10 | ASCF-H-L1-10-9V |
| | For 10 valve positions, size 10 | ASCF-H-L1-10-10V |
| | For 12 valve positions, size 10 | ASCF-H-L1-10-12V |
| | For 16 valve positions, size 10 | ASCF-H-L1-10-16V |
| | For 20 valve positions, size 10 | ASCF-H-L1-10-20V |
| | For 24 valve positions, size 10 | ASCF-H-L1-10-24V |
| | For 4 valve positions, size 14 | ASCF-H-L1-14-4V |
| | For 5 valve positions, size 14 | ASCF-H-L1-14-5V |
| | For 6 valve positions, size 14 | ASCF-H-L1-14-6V |
| | For 7 valve positions, size 14 | ASCF-H-L1-14-7V |
| | For 8 valve positions, size 14 | ASCF-H-L1-14-8V |
| | For 9 valve positions, size 14 | ASCF-H-L1-14-9V |
| | For 10 valve positions, size 14 | ASCF-H-L1-14-10V |
| | For 12 valve positions, size 14 | ASCF-H-L1-14-12V |
| | For 16 valve positions, size 14 | ASCF-H-L1-14-16V |
| For 20 valve positions, size 14 | ASCF-H-L1-14-20V | |
| For 24 valve positions, size 14 | ASCF-H-L1-14-24V | |