



# Modular controllers CECX

Key features



## At a glance

### Versatile

The controller is functionally designed as a master and motion controller. It is a powerful control unit that can

simultaneously execute both comprehensive PLC functions and multi-axis movements with interpolation.

### Economical

The modular structure offers the right solutions for all requirements. It has a high component density, is easy to

use and can be mounted on H-rails. It is fully compatible with all products from Festo and other manufacturers.

### Controlling electric axes

Simple commissioning, programming and servicing:  
With the SoftMotion module, the CoDeSys software offers a powerful programming environment

for controlling all electric axes with CANopen fieldbus connection. Additionally available: module libraries, configuration tools and drivers.

### Flexible

Programming to the IEC 61131-3 standard means the CECX is flexible and open for all types of control tasks. Numerous communication modules

(PROFIBUS, CANopen, Ethernet) guarantee compatibility with other systems.

### Reliable

It is certified to CE, UL/CSA, produced based on global experience in front end automation and uses standard hardware and CoDeSys standard software.

### Product features

- Two product versions
  - Modular master controller with CoDeSys
  - Motion controller with CoDeSys and SoftMotion
- Easy configuration
- Automatic module detection
- Search function for finding controllers in the network
- DHCP-compatible
- Automatic transfer of the communication settings to the project

## Module selection

### CPU unit

- Power PC 400 MHz
- Ethernet interface
- CAN-Bus interface
- RS 485 interface
- USB interface
- Compact Flash card as removable storage
- Slots for optional modules

### Optional modules

The controller CECX-X can be extended with the following optional modules:

- Ethernet interface
- CAN interface
- RS 232 serial interface
- RS 485-A/422-A serial interface

### Input/output modules

- Digital modules
- Analogue modules for current and voltage
- Temperature input modules
- Encoder counter modules

### Communication modules

- PROFIBUS master DP-V1
- PROFIBUS slave DP-V0
- PROFIBUS slave DP-V1
- 2x RS 232 serial interface


## Actuating electric axes from Festo via CANopen interface

- Motor controllers CMMP-AS for servo motors
- Motor controller CMMS-ST for stepper motors
- Motor controllers SFC-DC and SFC-LAC
- Motor unit MTR-DCI

# Modular controllers CECX

Key features

## Controller CECX with peripheral modules and optional modules



Type	Description	→ Page/Internet
<b>Peripheral modules</b>		
Input/output module, digital CECX-D-...E8A	<ul style="list-style-type: none"> <li>• 6 or 8 digital inputs</li> <li>• 8 digital outputs</li> </ul>	9
Input/output module, analogue CECX-A-4E4A-V	<ul style="list-style-type: none"> <li>• 4 analogue voltage inputs</li> <li>• 4 analogue voltage outputs</li> </ul>	11
Input/output module, analogue CECX-A-4E4A-A	<ul style="list-style-type: none"> <li>• 4 analogue current inputs</li> <li>• 4 analogue current outputs</li> </ul>	11
Input module, digital CECX-D-16E	<ul style="list-style-type: none"> <li>• 16 digital inputs</li> </ul>	14
Input module, analogue CECX-A-4E-V	<ul style="list-style-type: none"> <li>• 4 analogue voltage inputs</li> </ul>	16
Output module, digital CECX-D-14A-2	<ul style="list-style-type: none"> <li>• 14 digital outputs</li> </ul>	18
Output module, analogue CECX-A-4A-V	<ul style="list-style-type: none"> <li>• 4 analogue voltage outputs</li> </ul>	20
Input module, analogue CECX-E-...E-T-P...	<ul style="list-style-type: none"> <li>• 4 or 6 temperature inputs</li> </ul>	22
Encoder interface CECX-C-2G2/-2G1	<ul style="list-style-type: none"> <li>• 2 encoder inputs/4 encoder inputs SSI (RS 422)</li> </ul>	25
Bus interface CECX-F-PB-S-V...	<ul style="list-style-type: none"> <li>• PROFIBUS slave DP-V0</li> <li>• PROFIBUS slave DP-V1</li> </ul>	28
Bus interface CECX-F-PB-V1	<ul style="list-style-type: none"> <li>• PROFIBUS master DP-V1</li> </ul>	30
Bus interface CECX-B-CO	<ul style="list-style-type: none"> <li>• Connection via CAN bus to the modular controller</li> <li>• For connecting decentralised peripheral modules in series</li> </ul>	32
Electrical interface CECX-C-2S1	<ul style="list-style-type: none"> <li>• 2 RS 232 serial interfaces</li> </ul>	34
<b>Optional modules</b>		
Bus interface CECX-F-CO	<ul style="list-style-type: none"> <li>• CAN interface</li> </ul>	36
Electrical interface CECX-C-ET	<ul style="list-style-type: none"> <li>• Ethernet interface</li> </ul>	38
Electrical interface CECX-C-S1	<ul style="list-style-type: none"> <li>• RS 232 serial interface</li> </ul>	40
Electrical interface CECX-S-S4	<ul style="list-style-type: none"> <li>• RS 485-A/422-A serial interface</li> </ul>	40


- Note  
Max. 12 peripheral modules can be mounted. Mounting rules → System manual.

# Modular controllers CECX

Key features



## Type codes



Type	
CECX	Modular controller

Controller	
X	CPU

Control type	
C1	CoDeSys
M1	MotionControl

# Modular controllers CECX

Technical data

**Controller CECX-X-C1**  
Modular master controller with CoDeSys

**Controller CECX-X-M1**  
Motion controller with CoDeSys and SoftMotion

The controller is the central module in the modular control unit. It provides the resources for executing the application software.

The controller has three plug-in slots for optional modules to effect the following connections for interfaces:

- CAN bus interface
- Ethernet electrical interface
- RS 232 serial interface

The controller is equipped with the optional module for the Ethernet electrical interface by default.



General technical data		CECX-X-C1	CECX-X-M1
Operating voltage range	[V DC]	19.2 ... 30	
Power consumption at 24 V	[W]	14	
Max. power output at 5 V	[W]	10	
Max. power output at 24 V	[W]	45	
Max. power consumption	[W]	69	
Resistance to shock		EN 60068-2-27 EA	
		15 g, 11 ms (half sine)	
Resistance to vibration		EN 60068-2-6-FC	
		5 ... 9 Hz, 3.5 mm	
		9 ... 150 Hz, 1g	
Control elements		CTRL button	
CPU data		64 MB DRAM	
		400 MHz processor	
Programming software		CoDeSys provided by Festo	CoDeSys provided by Festo
		–	SoftMotion
Programming language		SFC, IL, FCH, LD and ST to IEC 61131-3	SFC, IL, FCH, LD and ST to IEC 61131-3
		Additionally CFC	Additionally CFC
Status displays		7-segment display	
		LED green = power	
Slots		1x CAN optional module → 36	
		1x Compact Flash type 1	
		1x Ethernet optional module → 38	
		1x serial interface module → 40	
USB interface		USB 1.1	
Protection class		IP20	
Electrical protection class		III	
Product weight	[g]	580	
<b>Materials</b>			
Note on materials		Contains PWIS (paint-wetting impairment substances)	
		RoHS-compliant	

# Modular controllers CECX


Technical data

FESTO

Technical data – Interfaces		CECX-X-C1	CECX-X-M1
<b>Ethernet</b>			
Connector plug		RJ45 socket, 8-pin	
Data transmission speed	[Mbps]	10/100	
Supported protocols		TCP/IP, EasyIP and Modbus TCP	
<b>Fieldbus interface</b>			
Type		CAN bus	
Connection technology		Sub-D plug, 9-pin	
Transmission rate	[kbps]	125; 250; 500; 800; 1,000 Adjustable via software	
Galvanic isolation		No	
<b>Serial interface</b>			
Type		RS 485-A	
Number		1	
Connection technology		Sub-D plug, 9-pin	
Transmission rate	[bps]	1,200 ... 115,000 Adjustable via software	
Galvanic isolation		No	

Operating and environmental conditions			
Ambient temperature	[°C]	+5 ... +55	
Storage temperature	[°C]	-40 ... +70	
Relative air humidity	[%]	10 ... 95	
CE mark (see declaration of conformity)		To EU EMC Directive	
Certification		cULus listed (OL)	


## Connection and display components





- 1 Operating voltage connection (X2)
- 2 RS 485 serial interface (X1)
- 3 7-segment display
- 4 Power LED
- 5 Ethernet interface (X5)
- 6 CAN interface (X6)
- 7 CAN status LEDs (TX, RX)
- 8 Compact Flash status LED
- 9 Compact Flash plug-in slot (X7)
- 10 USB interface (X8)

# Modular controllers CECX

Technical data

Pin allocation – RS 485 serial interface (X1)			
	Pin	Signal	Meaning
Sub-D plug			
	1	GND	Ground
	2	Therm B	Terminating resistor
	3	B / B'	Transmit/receive +
	4	n.c.	Not connected
	5	GND	Ground
	6	n.c.	Not connected
	7	Therm A	Terminating resistor
	8	A / A'	Transmit/receive –
	9	n.c.	Not connected

Pin allocation – Ethernet interface (X5)			
	Pin	Signal	Meaning
RJ45 plug			
	1	TD+	Transmitted data +
	2	TD–	Transmitted data –
	3	RD+	Received data +
	4	n.c.	Not connected
	5	n.c.	Not connected
	6	RD–	Received data –
	7	n.c.	Not connected
	8	n.c.	Not connected
	Housing	Screened	Screened

Pin allocation – CAN interface (X6)			
	Pin	Signal	Meaning
Sub-D plug			
	1	n.c.	Not connected
	2	CAN_L	CAN low
	3	SGND	Signal ground
	4	TERM1	Connection for activating the internal terminating resistor
	5	TERM1	Connection for activating the internal terminating resistor
	6	GND	Ground
	7	CAN_H	CAN high
	8	TERM2	Connection for activating the internal terminating resistor
	9	TERM2	Connection for activating the internal terminating resistor
Housing	Screened	Screened	





# Modular controllers CECX

Technical data

**Input/output module, digital  
CECX-D-...E8A**

There are 6 or 8 digital inputs and 8 digital outputs available for processing digital process signals.

The following functions are available:

- Address setting
- Short circuit monitoring for outputs
- Debounce function for inputs
- Interrupt function DI0 and DI1



General technical data		
Operating voltage range	[V DC]	19.2 ... 30
Electrical connection technology for I/O		Socket strip, grid 5.08 mm
Power consumption at 5 V	[W]	0.4
Power consumption at 24 V	[W]	1.9
Resistance to shock		EN 60068-2-27 EA
		15 g, 11 ms (half sine)
Resistance to vibration		EN 60068-2-6-FC
		5 ... 9 Hz, 3.5 mm
		9 ... 150 Hz, 1g
Protection class		IP20
Electrical protection class		III
Product weight	[g]	135
Materials		
Note on materials		Contains PWIS (paint-wetting impairment substances)
		RoHS-compliant

Technical data – Interfaces		
	CECX-D-6E8A-PN	CECX-D-8E8A-NP
Digital inputs		
Number	6	8
Fast clock pulse inputs	2, interruptible, response time 50 µs	
Input voltage/current	[V DC]	24
Nominal value for FALSE	[V DC]	≤ 5
Nominal value for TRUE	[V DC]	≥ 15
Input signal delay	[ms]	2, 100, adjustable
	[kHz]	12 with interrupt input
Electrical isolation	Yes, via optocoupler	
Status display	[V DC]	LED green
Switching logic	Negative logic (NPN)	Positive logic (PNP)
Digital outputs		
Number	8	
Contact	Transistor	
Output voltage	[V DC]	24
Output current	[A]	2 with 50% concurrence
Short circuit proof	Yes	
Electrical isolation	Yes, via optocoupler	
Status display	[V DC]	LED orange
Switching logic	Negative logic (NPN)	Positive logic (PNP)

# Modular controllers CECX


Technical data

FESTO

Operating and environmental conditions			
		CECX-D-6E8A-PN	CECX-D-8E8A-NP
Ambient temperature	[°C]	+5 ... +55	+5 ... +55
Storage temperature	[°C]	-40 ... +70	-40 ... +70
Relative air humidity	[%]	10 ... 95	10 ... 95
CE mark (see declaration of conformity)		-	To EU EMC Directive
Certification		c UL us - Listed (OL)	c UL us - Listed (OL)


## Connection and display components

CECX-D-6E8A-PN



- 1 Digital output or digital input status LEDs
- 2 Bus plug
- 3 Power supply for outputs
- 4 Digital output D00 ... D07
- 5 Power supply for inputs
- 6 Digital input DI0 ... DI5

CECX-D-8E8A-NP



- 1 Digital output or digital input status LEDs
- 2 Bus plug
- 3 Power supply
- 4 Digital output D00 ... D07
- 5 Digital input DI0 ... DI7


## Pin allocation

Pin	Designation	Meaning
Socket strip		
00	0 V	0 V power supply for outputs
01	24 V	24 V power supply for outputs
02 ... 09	D00 ... D07	Digital output 0 ... 7
10	0 V	0 V power supply for inputs
11	24 V	24 V power supply for inputs
12 ... 17	DI0 ... DI5 <sup>1)</sup>	Digital input 0 ... 5

Pin	Designation	Meaning
Socket strip		
00	0 V	0 V power supply
01	24 V	24 V power supply
02 ... 09	D00 ... D07	Digital output 0 ... 7
10 ... 17	DI0 ... DI7 <sup>1)</sup>	Digital input 0 ... 7

1) DI0, DI1: interrupt inputs

## Ordering data

Input/output module, digital	Part No.	Type
	553972	CECX-D-6E8A-PN-2
	552099	CECX-D-8E8A-NP-2

- Note

Accompanying manuals in German and English can be found on the CD-ROM supplied with the controller CECX-X.

# Modular controllers CECX

Technical data

**Input/output module, analogue  
CECX-A-4E4A-V**

4 analogue voltage inputs/outputs for processing analogue process signals.

The following function is available:

- Sensor failure detection

**Input/output module, analogue  
CECX-A-4E4A-A**

4 analogue current inputs/outputs for processing analogue process signals.



General technical data		CECX-A-4E4A-V	CECX-A-4E4A-A
Electrical connection technology for I/O		Socket strip, grid 5.08 mm	
Power consumption at 5 V	[W]	0.3	0.3
Power consumption at 24 V	[W]	3.3	3.6
Resistance to shock		EN 60068-2-27 EA 15 g, 11 ms (half sine)	
Resistance to vibration		EN 60068-2-6-FC 5 ... 9 Hz, 3.5 mm 9 ... 150 Hz, 1g	
Protection class		IP20	
Electrical protection class		III	
Product weight	[g]	135	
Materials			
Note on materials		Contains PWIS (paint-wetting impairment substances) RoHS-compliant	

Technical data – Interfaces		CECX-A-4E4A-V	CECX-A-4E4A-A
Analogue inputs			
Number		4	4
Resolution	[bit]	14	14
Signal range	[V]	0 ... 10 Vref ±10	–
	[mA]	–	0 ... 20 4 ... 20
Value of the least significant bit (LSB)	[mV]	1.3	–
	[µA]	–	1.35
Supply voltage for actuators	[V DC]	10 ±2.5% (max. 20 mA)	–
Input resistance	[Ω]	10 10 <sup>6</sup>	< 200
Absolute accuracy at 25 °C	[%]	±0.01	±0.01
Sampling repeat time	[ms]	1	1
Galvanic isolation		No	No
Analogue outputs			
Number		4	4
Resolution	[bit]	12	12
Max. load resistance	[Ω]	≥ 1,000	≤ 600
Signal range	[V]	±10	–
	[mA]	–	0 ... 20
Value of the least significant bit (LSB)	[mV]	5.32	–
	[µA]	–	5.39
Conversion time	[ms]	1	1
Absolute accuracy at 25 °C	[%]	±0.15	±0.15


# Modular controllers CECX

Technical data

FESTO

Operating and environmental conditions	
Ambient temperature [°C]	+5 ... +55
Storage temperature [°C]	-40 ... +70
Relative air humidity [%]	10 ... 95
CE mark (see declaration of conformity)	To EU EMC Directive
Certification	c UL us - Listed (OL)

## Connection and display components





- 1 Bus plug
- 2 Analogue input AI0 ... AI7
- 3 Analogue output A00 ... A07

Pin allocation			
Pin	Designation	Meaning	
		CECX-A-4E4A-V	CECX-A-4E4A-A
Socket strip			
00	V <sub>REF</sub> / n.c.	Reference voltage	Not connected
01	AI0+	Positive voltage input signal AI0	Positive current input signal AI0
02	AI0-	Negative voltage input signal AI0	Negative current input signal AI0
03	AI1+	Positive voltage input signal AI1	Positive current input signal AI1
04	AI1-	Negative voltage input signal AI1	Negative current input signal AI1
05	GND	Reference potential GND	Reference potential GND
06	AI2+	Positive voltage input signal AI2	Positive current input signal AI2
07	AI2-	Negative voltage input signal AI2	Negative current input signal AI2
08	AI3+	Positive voltage input signal AI3	Positive current input signal AI3
09	AI3-	Negative voltage input signal AI3	Negative current input signal AI3
10	GND	Reference potential GND	Reference potential GND
11	A00	Voltage output signal A00	Current output signal A00
12	A01	Voltage output signal A01	Current output signal A01
13	GND	Reference potential GND	Reference potential GND
14	A02	Voltage output signal A02	Current output signal A02
15	A03	Voltage output signal A03	Current output signal A03
16	GND	Reference potential GND	Reference potential GND
17	GND	Reference potential GND	Reference potential GND

# Modular controllers CECX

Technical data

Ordering data			
Input/output module, analogue		Part No.	Type
	With 4 analogue voltage inputs/outputs	552100	CECX-A-4E4A-V
	With 4 analogue current inputs/outputs	552101	CECX-A-4E4A-A

-  - Note  
Accompanying manuals in German and English can be found on the CD-ROM supplied with the controller CECX-X.

# Modular controllers CECX

Technical data

FESTO

## Input module, digital

### CECX-D-16E

There are 16 digital inputs available for processing digital process signals.



General technical data	
Electrical connection technology for I/O	Socket strip, grid 5.08 mm
Power consumption at the system bus [W]	0.4
Resistance to shock	EN 60068-2-27 EA 15 g, 11 ms (half sine)
Resistance to vibration	EN 60068-2-6-FC 5 ... 9 Hz, 3.5 mm 9 ... 150 Hz, 1g
Protection class	IP20
Electrical protection class	III
Product weight [g]	130
Materials	
Note on materials	Contains PWIS (paint-wetting impairment substances) RoHS-compliant


Technical data – Interface	
Digital inputs	
Number	16
Fast clock pulse inputs	2, interruptible, response time 100 µs
Input voltage/current [V DC]	24
Nominal value for FALSE [V DC]	≤ 5
Nominal value for TRUE [V DC]	≥ 15
Input signal delay [ms]	20, 200, adjustable Additionally 0.2 ms with interrupt inputs
Electrical isolation	Yes, via optocoupler
Status display [V DC]	LED
Switching logic	Positive logic (PNP)

Operating and environmental conditions	
Ambient temperature [°C]	+5 ... +55
Storage temperature [°C]	-40 ... +70
Relative air humidity [%]	10 ... 95

# Modular controllers CECX

Technical data

## Connection and display components




- 1 Digital input status LEDs
- 2 Bus plug
- 3 Reference potential
- 4 Digital input DI0 ... DI15

### Pin allocation

Pin	Designation	Meaning
Socket strip		
00	0 V	Reference potential
01	n.c.	Not connected
02 ... 17	DI0 ... DI15	Digital input 0 ... 15 <sup>1)</sup>

1) DI0 and DI1 are interruptible

### Ordering data

Input module, digital	Part No.	Type
 With 16 digital inputs	552096	CECX-D-16E

-  Note

Accompanying manuals in German and English can be found on the CD-ROM supplied with the controller CECX-X.

# Modular controllers CECX

## Technical data

### Input module, analogue CECX-A-4E-V

There are 4 analogue voltage inputs available for processing analogue process signals.

The following function is available:

- Sensor failure detection



General technical data		
Electrical connection technology for I/O		Socket strip, grid 5.08 mm
Power consumption at 5 V	[W]	0.3
Power consumption at 24 V	[W]	2
Resistance to shock		EN 60068-2-27 EA 15 g, 11 ms (half sine)
Resistance to vibration		EN 60068-2-6-FC 5 ... 9 Hz, 3.5 mm 9 ... 150 Hz, 1g
Protection class		IP20
Electrical protection class		III
Product weight	[g]	132
Materials		
Note on materials		Contains PWIS (paint-wetting impairment substances) RoHS-compliant

Technical data – Interfaces		
Analogue inputs		
Number		4
Resolution	[bit]	14
Signal range	[V]	0 ... 10 Vref
	[V]	±10
Value of the least significant bit (LSB)	[mV]	1.3
Supply voltage for actuators	[V DC]	10 ±2.5 % (max. 20 mA)
Input resistance	[MΩ]	10
Absolute accuracy at 25 °C	[%]	±0.01
Sampling repeat time	[ms]	1
Galvanic isolation		No

Operating and environmental conditions		
Ambient temperature	[°C]	+5 ... +55
Storage temperature	[°C]	-40 ... +70
Relative air humidity	[%]	10 ... 95
Certification		cULus listed (OL)




# Modular controllers CECX

Technical data


FESTO


## Connection and display components



- 1 Bus plug
- 2 Analogue voltage input AI0 ... AI3

Pin allocation		
Pin	Designation	Meaning
Socket strip		
00	V <sub>REF</sub> / n.c.	Reference voltage
01	AI0+	Pos. voltage input signal AI0
02	AI0-	Neg. voltage input signal AI0
03	AI1+	Pos. voltage input signal AI1
04	AI1-	Neg. voltage input signal AI1
05	GND	Reference potential GND
06	AI2+	Pos. voltage input signal AI2
07	AI2-	Neg. voltage input signal AI2
08	AI3+	Pos. voltage input signal AI3
09	AI3-	Neg. voltage input signal AI3
10	GND	Reference potential GND
11	n.c.	Not connected
12	n.c.	Not connected
13	n.c.	Not connected
14	n.c.	Not connected
15	n.c.	Not connected
16	GND	Reference potential GND
17	GND	Reference potential GND

Ordering data		
Input module, analogue	Part No.	Type
	With 4 analogue voltage inputs	<b>553975</b> <b>CECX-A-4E-V</b>

-  - Note  
 Accompanying manuals in German and English can be found on the CD-ROM supplied with the controller CECX-X.

# Modular controllers CECX

Technical data

FESTO

## Output module, digital

### CECX-D-14A-2

There are 14 digital outputs available for processing digital process signals.



General technical data		
Operating voltage range	[V DC]	24 +25%/–15%
Electrical connection technology for I/O		Socket strip, grid 5.08 mm
Power consumption at the system bus	[W]	0.4
Resistance to shock		EN 60068-2-27 EA 15 g, 11 ms (half sine)
Resistance to vibration		EN 60068-2-6-FC 5 ... 9 Hz, 3.5 mm 9 ... 150 Hz, 1g
Protection class		IP20
Electrical protection class		III
Product weight	[g]	135
Materials		
Note on materials		Contains PWIS (paint-wetting impairment substances) RoHS-compliant


Technical data – Interface		
Digital outputs		
Number		14
Contact		Transistor
Output voltage	[V DC]	24
Output current	[A]	2 with 50% concurrence per group
Short circuit proof		Yes
Electrical isolation		Yes, via optocoupler
Electrical isolation in groups		Yes, in 2 groups
Status display	[V DC]	LED
Switching logic		Positive logic (PNP)

Operating and environmental conditions		
Ambient temperature	[°C]	+5 ... +55
Storage temperature	[°C]	–40 ... +70
Relative air humidity	[%]	10 ... 95

# Modular controllers CECX

Technical data

## Connection and display components




- 1 Digital output status LEDs
- 2 Bus plug
- 3 Voltage supply for D00 ... D07
- 4 Digital output D00 ... D07
- 5 Voltage supply for D08 ... D013
- 6 Digital output D08 ... D013

### Pin allocation

Pin	Designation	Meaning
Socket strip – group 1		
00	0 V	0 V voltage supply for D00 ... D07
01	+24 V	24 V voltage supply for D00 ... D07
02 ... 09	D00 ... D07	Digital output 0 ... 7
Socket strip – group 2		
10	0 V	0 V voltage supply for D08 ... D013
11	+24 V	24 V voltage supply for D08 ... D013
12 ... 17	D08 ... D013	Digital output 8 ... 13

### Ordering data

Output module, digital	Part No.	Type
 With 14 digital outputs	<b>552097</b>	<b>CECX-D-14A-2</b>

### Note

Accompanying manuals in German and English can be found on the CD-ROM supplied with the controller CECX-X.

# Modular controllers CECX

Technical data

**Output module, analogue  
CECX-A-4A-V**

There are 4 analogue voltage outputs available for processing analogue process signals.

The following function is available:

- Sensor failure detection



General technical data		
Electrical connection technology for I/O		Socket strip, grid 5.08 mm
Power consumption at 5 V	[W]	0.3
Power consumption at 24 V	[W]	1.9
Resistance to shock		EN 60068-2-27 EA
		15 g, 11 ms (half sine)
Resistance to vibration		EN 60068-2-6-FC
		5 ... 9 Hz, 3.5 mm
		9 ... 150 Hz, 1g
Protection class		IP20
Electrical protection class		III
Product weight	[g]	132
Materials		
Note on materials		Contains PWIS (paint-wetting impairment substances) RoHS-compliant


Technical data – Interfaces		
Analogue outputs		
Number		4
Resolution	[bit]	12
Max. load resistance	[Ω]	≥ 1,000
Signal range	[V]	±10
Value of the least significant bit (LSB)	[mV]	5.32
Conversion time	[ms]	1
Absolute accuracy at 25 °C	[%]	±0.15

Operating and environmental conditions		
Ambient temperature	[°C]	+5 ... +55
Storage temperature	[°C]	-40 ... +70
Relative air humidity	[%]	10 ... 95
Certification		cULus listed (OL)

# Modular controllers CECX


Technical data

## Connection and display components



- 1 Bus plug
- 2 Analogue voltage output A00 ... A03

Pin allocation		
Pin	Designation	Meaning
Socket strip		
00	n.c.	Not connected
01	n.c.	Not connected
02	n.c.	Not connected
03	n.c.	Not connected
04	n.c.	Not connected
05	n.c.	Not connected
06	n.c.	Not connected
07	n.c.	Not connected
08	n.c.	Not connected
09	n.c.	Not connected
10	n.c.	Not connected
11	A00	Voltage output signal A00
12	A01	Voltage output signal A01
13	GND	Reference potential GND
14	A02	Voltage output signal A02
15	A03	Voltage output signal A03
16	GND	Reference potential GND
17	GND	Reference potential GND

Ordering data		
Output module, analogue	Part No.	Type
	With 4 analogue voltage outputs	<b>553976</b> <b>CECX-A-4A-V</b>

- Note  
 Accompanying manuals in German and English can be found on the CD-ROM supplied with the controller CECX-X.

# Modular controllers CECX

Technical data

## Input module, analogue

### CECX-E-4E-T-P1

There are 4 temperature inputs available for the temperature sensor PT 100.

The following function is available:

- 2-wire and 4-wire connection


## Input module, analogue

### CECX-E-6E-T-P2

There are 6 temperature inputs available for the thermoelement type J, K and L.

The following function is available:

- Internal and external cold junction compensation



General technical data		CECX-E-4E-T-P1	CECX-E-6E-T-P2
Electrical connection technology for I/O		Socket strip, grid 5.08 mm	Gold contacts
Power consumption at 5 V	[W]	0.3	0.6
Power consumption at 24 V	[W]	2.5	1.6
Resistance to shock		EN 60068-2-27 EA 15 g, 11 ms (half sine)	
Resistance to vibration		EN 60068-2-6-FC 5 ... 9 Hz, 3.5 mm 9 ... 150 Hz, 1g	
Protection class		IP20	
Electrical protection class		III	
Product weight	[g]	134	142
Materials			
Note on materials		Contains PWIS (paint-wetting impairment substances) RoHS-compliant	

Technical data – Interfaces		CECX-E-4E-T-P1	CECX-E-6E-T-P2
Analogue inputs			
Number		4	6
Resolution	[bit]	14	
Signal range		PT100 (-100 ... +850 °C)	Thermoelement
		–	Type J (Fe-CuNi, -100 ... +700 °C)
		–	Type K (NiCr-Ni, -100 ... +1,000 °C)
		–	Type L (Fe-CuNi, -100 ... +700 °C)
Value of the least significant bit (LSB)	[°C]	0.058	–
Input resistance	[Ω]	10 10 <sup>6</sup>	> 10 10 <sup>3</sup>
Absolute accuracy at 25 °C	[%]	±0.01	± 1.0 °C
Internal cycle time	[ms]	2	100
Galvanic isolation		No	Yes


Operating and environmental conditions		
Ambient temperature	[°C]	+5 ... +55
Storage temperature	[°C]	-40 ... +70
Relative air humidity	[%]	10 ... 95
Certification		cULus listed (OL)

# Modular controllers CECX

Technical data


## Connection and display components

CECX-E-4E-T-P1



- 1 Bus plug
- 2 Analogue input for temperature sensor AI0 ... AI3

CECX-E-6E-T-P2



- 1 Bus plug
- 2 Analogue input for temperature sensor TI0 ... TI5
- 3 Sensor interface for external temperature compensation



### Pin allocation


Pin	Designation	Meaning
Socket strip		
00	IRF 0	
01	AI0+	Temperature sensor0 +
02	AI0-	Temperature sensor0 -
03	GND	Reference potential GND
04	IRF 1	
05	AI1+	Temperature sensor1 +
06	AI1-	Temperature sensor1 -
07	GND	Reference potential GND
08	IRF 2	
09	AI2+	Temperature sensor2 +
10	AI2-	Temperature sensor2 -
11	GND	Reference potential GND
12	IRF 3	
13	AI3+	Temperature sensor3 +
14	AI3-	Temperature sensor3 -
15	GND	Reference potential GND
16	GND	Reference potential GND
17	GND	Reference potential GND

Pin	Designation	Meaning
Socket strip		
00	+TI0	Temperature sensor0 +
01	- TI0	Temperature sensor0 -
02	+TI1	Temperature sensor1 +
03	- TI1	Temperature sensor1 -
04	+TI2	Temperature sensor2 +
05	- TI2	Temperature sensor2 -
06	+TI3	Temperature sensor3 +
07	- TI3	Temperature sensor3 -
08	+TI4	Temperature sensor4 +
09	- TI4	Temperature sensor4 -
10	+TI5	Temperature sensor5 +
11	- TI5	Temperature sensor5 -

# Modular controllers CECX

Technical data

Ordering data		Part No.	Type
 Input module, analogue	With 4 temperature inputs for the temperature sensor PT 100	553973	CECX-E-4E-T-P1
 Input module, analogue	With 6 temperature inputs for the thermoelements type J, K and L	553974	CECX-E-6E-T-P2

-  - Note  
Accompanying manuals in German and English can be found on the CD-ROM supplied with the controller CECX-X.



# Modular controllers CECX

Technical data

## Encoder interface

### CECX-C-2G2

The following functions are available:

- Displacement measurement: incremental/decremental counter (displacement measurement) using A and B track, 1-way, 2-way, 4-way evaluation, 32-bit resolution
- Pulse counter on track A, 32-bit resolution
- Pulse counter on track A with direction evaluation for track B, 32-bit resolution
- Speed measurement by means of sampling with internal time basis

- Shaft encoder monitoring using zero-track information
- Counter reading latch function via an external latch input
- Counter reading latch function via zero pulse
- Sensor rupture monitoring for tracks A, B and zero

## Encoder interface

### CECX-C-2G1

The following function is available:

- Power/receive status display
- Binary/grey signal range



General technical data		CECX-C-2G2	CECX-C-2G1
Operating voltage range	[V DC]	19.2 ... 30	
Electrical connection technology for I/O		Socket strip, grid 5.08 mm	
Power consumption at 5 V	[W]	0.6	0.65
Resistance to shock		EN 60068-2-27 EA	
		15 g, 11 ms (half sine)	
Resistance to vibration		EN 60068-2-6-FC	
		5 ... 9 Hz, 3.5 mm	
		9 ... 150 Hz, 1g	
Status displays			LED green = power LED yellow = receive
Protection class		IP20	
Electrical protection class		III	
Product weight	[g]	135	140
<b>Materials</b>			
Note on materials		Contains PWIS (paint-wetting impairment substances)	
		RoHS-compliant	

Technical data – Interfaces		CECX-C-2G2	CECX-C-2G1
<b>Digital inputs</b>			
Fast clock pulse inputs		2 (latch) response time 20 µs NPN/PNP	–
Electrical isolation		No	–
<b>Encoder inputs</b>			
Number		2	4
Connection technology		Sub-D socket, 9-pin	RJ45
Resolution	[bit]	Speed measurement: 32	16 ... 32
	[bit]	Displacement measurement: 24	Adjustable via software
Encoder supply voltage	[V DC]	24	24 (250 mA/channel)
	[V DC]	5.05 ±4 % (100 mA/channel)	–
Max. input frequency	[kHz]	250	–
Baud rate	[kbps]	–	125; 250; 500; 1,000
			Adjustable via software
Signal range		5 differential (RS 422)	SSI (RS 422)
		24 single-ended	Binary/grey can be set using software
Galvanic isolation		–	No

# Modular controllers CECX

Technical data




Operating and environmental conditions			
		CECX-C-2G2	CECX-C-2G1
Ambient temperature	[°C]	+5 ... +55	+5 ... +55
Storage temperature	[°C]	-40 ... +70	-40 ... +70
Relative air humidity	[%]	10 ... 95	10 ... 95
CE mark (see declaration of conformity)		To EU EMC Directive	-
Certification		c UL us - Listed (OL)	c UL us - Listed (OL)


## Connection and display components

CECX-C-2G2

CECX-C-2G1



- 1 Bus plug
- 2 Power supply
- 3 Latch inputs
- 4 Encoder input X2
- 5 Encoder input X3





- 1 LED
- 2 LED
- 3 Bus plug
- 4 Power supply
- 5 SSI interface SSI0 ... SSI3

## Pin allocation

	Pin	Signal	Meaning	
			Signal range 5 V	Signal range 24 V
<b>Sub-D socket</b>				
	1	GND	Ground	
	2	24 V	Encoder supply	
	3	0+	Zero track+	
	4	B+	Track B+	
	5	A+	Track A+	
	6	5 V (max. 100 mA)	Encoder supply	
	7	0-	Zero track-	Do not connect
	8	B-	Track B-	Do not connect
	9	A-	Track A-	Do not connect
<b>RJ45 socket</b>				
	1	n.c.	Not connected	
	2	n.c.	Not connected	
	3	DI+	Data input +	
	4	CK-	Clock input -	
	5	CK+	Clock input +	
	6	DI-	Data input -	
	7	24 V	Encoder supply	
	8	0 V	Encoder supply	

# Modular controllers CECX

Technical data

Ordering data			
Encoder interface		Part No.	Type
	With 2 encoder inputs	552117	CECX-C-2G2
	With 4 encoder inputs SSI (RS 422)	553977	CECX-C-2G1

-  - Note

Accompanying manuals in German and English can be found on the CD-ROM supplied with the controller CECX-X.

# Modular controllers CECX

Technical data



## Bus interface

### CECX-F-PB-S-V...

The modular controller can be connected to the PROFIBUS DP-V0 or to the PROFIBUS DP-V1 as a slave using this peripheral module.



General technical data		
Power consumption at 5 V	[W]	1.4
Resistance to shock		EN 60068-2-27 EA
		15 g, 11 ms (half sine)
Resistance to vibration		EN 60068-2-6-FC
		5 ... 9 Hz, 3.5 mm
		9 ... 150 Hz, 1g
Status displays		LED (status)
		LED red = bus fault
Protection class		IP20
Electrical protection class		III
Product weight	[g]	140
Materials		
Note on materials		Contains PWIS (paint-wetting impairment substances)
		RoHS-compliant


Technical data – Interface		
CECX-F-PB-S-	V0	V1
Fieldbus		
Type	PROFIBUS slave DP-V0	PROFIBUS slave DP-V1
Connection technology	Sub-D socket, 9-pin	
Transmission rate	9.6 kbps ... 12 Mbps	
Galvanic isolation	Yes	

Operating and environmental conditions		
CECX-F-PB-S-	V0	V1
Ambient temperature	[°C]	+5 ... +55
Storage temperature	[°C]	-40 ... +70
Relative air humidity	[%]	10 ... 95
CE mark (see declaration of conformity)	To EU EMC Directive	-
Certification	c UL us - Listed (OL)	

# Modular controllers CECX

Technical data

## Connection and display components



- 1 Bus plug
- 2 Bus fault LED
- 3 Status LED
- 4 PROFIBUS interface
- 5 DIP switch

## Pin allocation

	Pin	Signal	Meaning
<b>Sub-D socket</b>			
	3	RxD/TxD-P	Received/transmitted data P, B cable
	4	RTS	Signal is HIGH if module is sending data
	5	GND	Ground (galvanically isolated)
	6	5 V	5 V (galvanically isolated)
	8	RxD/TxD-N	Received/transmitted data N, A cable

## Ordering data

Bus interface		Part No.	Type
	As a slave to the PROFIBUS DP-V0	<b>552102</b>	<b>CECX-F-PB-S-V0</b>
	As a slave to the PROFIBUS DP-V1	<b>565598</b>	<b>CECX-F-PB-S-V1</b>

## Note

Accompanying manuals in German and English can be found on the CD-ROM supplied with the controller CECX-X.

# Modular controllers CECX

Technical data

FESTO

## Bus interface

### CECX-F-PB-V1

The modular controller can be connected to the PROFIBUS DP-V1 as a master using this peripheral module.



General technical data		
Power consumption at 5 V	[W]	2
Resistance to shock		EN 60068-2-27 EA
		15 g, 11 ms (half sine)
Resistance to vibration		EN 60068-2-6-FC
		5 ... 9 Hz, 3.5 mm
		9 ... 150 Hz, 1g
Status displays		LED yellow = RDY, STA
		LED green = RUN
		LED red = ERR
Protection class		IP20
Electrical protection class		III
Product weight	[g]	138
Materials		
Note on materials		Contains PWIS (paint-wetting impairment substances)
		RoHS-compliant


Technical data – Interface	
Fieldbus	
Type	PROFIBUS master DP-V1
Connection technology	Sub-D socket, 9-pin
Transmission rate	9.6 kbps ... 12 Mbps
	Adjustable via software
Galvanic isolation	Yes

Operating and environmental conditions		
Ambient temperature	[°C]	+5 ... +55
Storage temperature	[°C]	-40 ... +70
Relative air humidity	[%]	10 ... 95
Certification		cULus listed (OL)

# Modular controllers CECX

Technical data

## Connection and display components



- 1 Bus plug
- 2 Error LED
- 3 Power LED
- 4 Run LED
- 5 Status LED
- 6 PROFIBUS interface

## Pin allocation

	Pin	Signal	Meaning
Sub-D socket			
	3	RxD/TxD-P	RS-485-A: B cable
	5	GND	Ground (galvanically isolated)
	6	5 V	5 V (galvanically isolated)
	8	RxD/TxD-N	RS-485-A: A cable

## Ordering data

Bus interface	Part No.	Type
	As a master to the PROFIBUS DP-V1	<b>553981 CECX-F-PB-V1</b>

## Note

Accompanying manuals in German and English can be found on the CD-ROM supplied with the controller CECX-X.

# Modular controllers CECX

Technical data



## Bus interface

### CECX-B-CO

The peripheral module is connected to the modular connector via CAN bus. Decentralised modules can then be connected in series to this module.



General technical data		
Operating voltage range	[V DC]	19.2 ... 30
Power consumption at 24 V	[W]	6.5
Resistance to shock		EN 60068-2-27 EA
		15 g, 11 ms (half sine)
Resistance to vibration		EN 60068-2-6-FC
		5 ... 9 Hz, 3.5 mm
		9 ... 150 Hz, 1g
Status displays		LED (status)
		LED yellow = transmit
		LED green = receive
Protection class		IP20
Electrical protection class		III
Product weight	[g]	121
Materials		
Note on materials		Contains PWIS (paint-wetting impairment substances)
		RoHS-compliant

Technical data – Interface		
Fieldbus		
Type		CAN bus
Connection technology		Sub-D plug, 9-pin
Transmission rate		125; 250; 500; 800; 1,000 kbps
		Can be adjusted using rotary switch
Galvanic isolation		No
Electrical connection technology for I/O		Socket strip, grid 5.08 mm
Output voltage/power output	[W]	24 V: 45
		5 V: 8.5


Operating and environmental conditions		
Ambient temperature	[°C]	+5 ... +55
Storage temperature	[°C]	-40 ... +70
Relative air humidity	[%]	10 ... 95
Certification		cULus listed (OL)



# Modular controllers CECX

Technical data

## Connection and display components



- 1 TX yellow LED
- 2 Status LED
- 3 Rotary switch for address setting
- 4 Rotary switch for transmission rate
- 5 CAN interface
- 6 RX green LED
- 7 Power supply

## Pin allocation

	Pin	Signal	Meaning
Sub-D plug			
	1	n.c.	Not connected
	2	CAN_L	CAN low
	3	SGND	Signal ground
	4	TERM1	Connection for activating the internal terminating resistor
	5	TERM1	Connection for activating the internal terminating resistor
	6	GND	Ground
	7	CAN_H	CAN high
	8	TERM2	Connection for activating the internal terminating resistor
	9	TERM2	Connection for activating the internal terminating resistor
	Housing	Screened	Screened

## Ordering data

Bus interface		Part No.	Type
	To the CAN bus	553980	CECX-B-CO

## Note

Accompanying manuals in German and English can be found on the CD-ROM supplied with the controller CECX-X.

# Modular controllers CECX

Technical data

FESTO

## Electrical interface

### CECX-S-2S1

Peripheral module for extending the controller with two RS 232 serial interfaces.




General technical data		CECX-S-2S1
Type		RS 232
Number		2
Connection technology		Sub-D plug, 9-pin
Transmission rate	[bps]	1,200 ... 115,000 Adjustable via software
Power consumption at 5 V	[W]	0.4
Resistance to shock		EN 60068-2-27 EA 15 g, 11 ms (half sine)
Resistance to vibration		EN 60068-2-6-FC 5 ... 9 Hz, 3.5 mm 9 ... 150 Hz, 1g
Status display		LED (status)
Galvanic isolation		No
Protection class		IP20
Electrical protection class		III
Product weight	[g]	132
Materials		
Note on materials		Contains PWIS (paint-wetting impairment substances) RoHS-compliant

Operating and environmental conditions		
Ambient temperature	[°C]	+5 ... +55
Storage temperature	[°C]	-40 ... +70
Relative air humidity	[%]	10 ... 95
Certification		cULus listed (OL)

# Modular controllers CECX

Technical data

## Connection and display components



1 RS 232 connection

### Pin allocation

	Pin	Signal	Meaning
Sub-D plug			
	1	n.c.	Not connected
	2	RxD	Receive data (input)
	3	TxD	Transmit data (output)
	4	n.c.	Not connected
	5	GND	Ground
	6	n.c.	Not connected
	7	RTS	Request to send (output)
	8	CTS	Clear to send (input)
	9	n.c.	Not connected
	Housing	Screened	Screened

### Ordering data

Electrical interface	Part No.	Type
	553978	CECX-S-2S1

# Modular controllers CECX

Technical data

## Bus interface

### CECX-F-CO

Optional module for extending the controller with a CAN interface.




General technical data	
Resistance to shock	EN 60068-2-27 EA 15 g, 11 ms (half sine)
Resistance to vibration	EN 60068-2-6-FC 5 ... 9 Hz, 3.5 mm 9 ... 150 Hz, 1g
Status displays	LED yellow = transmit LED green = receive
Electrical protection class	III
Product weight [g]	27
Materials	
Note on materials	Contains PWIS (paint-wetting impairment substances) RoHS-compliant

Technical data – Interface	
Fieldbus	
Type	CAN bus
Connection technology	Sub-D plug, 9-pin
Transmission rate	125; 250; 500; 800; 1,000 kbps Adjustable via software
Galvanic isolation	No

Operating and environmental conditions	
Ambient temperature [°C]	+5 ... +55
Storage temperature [°C]	-40 ... +70
Relative air humidity [%]	10 ... 95
CE mark (see declaration of conformity)	To EU EMC Directive
Certification	c UL us - Listed (OL)


## Connection and display components




- 1 CAN interface
- 2 TX yellow LED
- 3 RX green LED

# Modular controllers CECX

Technical data

Pin allocation			
	Pin	Signal	Meaning
Sub-D plug			
	1	n.c.	Not connected
	2	CAN_L	CAN low
	3	SGND	Signal ground
	4	TERM1	Connection for activating the internal terminating resistor
	5	TERM1	Connection for activating the internal terminating resistor
	6	GND	Ground
	7	CAN_H	CAN high
	8	TERM2	Connection for activating the internal terminating resistor
	9	TERM2	Connection for activating the internal terminating resistor
	Housing	Screened	Screened

Ordering data			
Bus interface		Part No.	Type
	CAN interface	553854	CECX-F-CO

# Modular controllers CECX

Technical data

## Electrical interface

### CECX-C-ET


Optional module for extending the controller with an Ethernet interface.



General technical data		
Connector plug		RJ45 socket, 8-pin
Data transmission speed	[Mbps]	10/100
Supported protocols		TCP/IP, EasyIP and Modbus TCP
Power consumption at the system bus	[W]	0.5
Resistance to shock		EN 60068-2-27 EA 15 g, 11 ms (half sine)
Resistance to vibration		EN 60068-2-6-FC 5 ... 9 Hz, 3.5 mm 9 ... 150 Hz, 1g
Status displays		LED yellow = transmit/receive LED green = link
Electrical protection class		III
Product weight	[g]	23
Materials		
Note on materials		Contains PWIS (paint-wetting impairment substances) RoHS-compliant


Operating and environmental conditions		
Ambient temperature	[°C]	+5 ... +55
Storage temperature	[°C]	-40 ... +70
Relative air humidity	[%]	10 ... 95
Certification		cULus listed (OL)


## Connection and display components



# Modular controllers CECX

Technical data

Pin allocation			
	Pin	Signal	Meaning
RJ45 socket			
	1	TD+	Transmitted data +
	2	TD-	Transmitted data -
	3	RD+	Received data +
	4	n.c.	Not connected
	5	n.c.	Not connected
	6	RD-	Received data -
	7	n.c.	Not connected
	8	n.c.	Not connected
	Metal covering	Screened	Screened

Ordering data			
Electrical interface		Part No.	Type
	Ethernet interface	553856	CECX-C-ET

# Modular controllers CECX

Technical data

FESTO

## Electrical interface CECX-C-S1

Optional module for extending the controller with an RS 232 serial interface.

## Electrical interface CECX-S-S4


Optional module for extending the controller with an RS 485-A/422-A serial interface.




General technical data		
	CECX-C-S1	CECX-S-S4
Type	RS 232	RS 485-A/422-A
Connection technology	Sub-D plug, 9-pin	
Transmission rate [bps]	1,200 ... 115,000 Adjustable via software	
Power consumption at the system bus [W]	0.2	-
Resistance to shock	EN 60068-2-27 EA 15 g, 11 ms (half sine)	
Resistance to vibration	EN 60068-2-6-FC 5 ... 9 Hz, 3.5 mm 9 ... 150 Hz, 1g	
Galvanic isolation	No	No
Protection class	-	IP20
Electrical protection class	III	III
Product weight [g]	31	31
Materials		
Note on materials	Contains PWIS (paint-wetting impairment substances) RoHS-compliant	

Operating and environmental conditions		
Ambient temperature [°C]	+5 ... +55	
Storage temperature [°C]	-40 ... +70	
Relative air humidity [%]	10 ... 95	
Certification	cULus listed (OL)	

## Connection and display components



1 RS 232 connection




1 RS 485-A/422-A connection




# Modular controllers CECX

Technical data

FESTO




Pin allocation – Sub-D plug			
	Pin	Signal	Meaning
	RS 232		
	1	n.c.	Not connected
	2	RxD	Receive data (input)
	3	TxD	Transmit data (output)
	4	n.c.	Not connected
	5	GND	Ground
	6	n.c.	Not connected
	7	RTS	Request to send (output)
	8	CTS	Clear to send (input)
	9	n.c.	Not connected
	Housing	Screened	Screened
	RS 485-A		
	1	GND	Ground
	2	Term B	Terminating resistor
	3	B / B'	Transmit/receive +
	4	n.c.	Not connected
	5	GND	Ground
	6	n.c.	Not connected
	7	Term A	Terminating resistor
	8	A / A'	Transmit/receive –
	9	n.c.	Not connected
	Housing	Screened	Screened
	RS 422-A		
	1	GND	Ground
	2	Term B	Terminating resistor
	3	B'	Receive +
	4	B	Transmit +
	5	GND	Ground
	6	n.c.	Not connected
	7	Term A	Terminating resistor
8	A'	Receive –	
9	A	Transmit –	
Housing	Screened	Screened	

Ordering data			
Electrical interface		Part No.	Type
	RS 232 serial interface	553855	CECX-C-S1
	RS 485-A/422-A serial interface	553979	CECX-S-S4

# Modular controllers CECX

Accessories

**FESTO**

Ordering data			
	Brief description	Part No.	Type
<b>Plug</b>			
	Plug for peripheral modules, 2-pin	<b>553857</b>	<b>NECC-L1G2-C1</b>
	Plug for peripheral modules, 4-pin	<b>553858</b>	<b>NECC-L1G4-C1</b>
	Plug for peripheral modules, 6-pin	<b>553859</b>	<b>NECC-L1G6-C1</b>
	Plug for peripheral modules, 8-pin	<b>553860</b>	<b>NECC-L1G8-C1</b>
	Plug for peripheral modules, 18-pin	<b>553861</b>	<b>NECC-L1G18-C1</b>
	Plug for PROFIBUS interface, Sub-D, 9-pin, without terminating resistor	<b>533780</b>	<b>FBS-SUB-9-WS-PB-K</b>
	Plug for CAN-Bus interface, Sub-D, 9-pin, without terminating resistor	<b>533783</b>	<b>FBS-SUB-9-WS-CO-K</b>
<b>Cable</b>			
	Cable for connecting an FED via RS 485 Cable length 2.5 m Straight socket, Sub-D, 15-pin Straight socket, Sub-D, 9-pin	<b>563782</b>	<b>NEBC-S1G15-K-2.5-N-B-S1G9-V</b>

## Product Range and Company Overview

### A Complete Suite and Company Overview

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



**Custom Automation Components**  
Complete custom engineered solutions



**Custom Control Cabinets**  
Comprehensive engineering support and on-site services



**Complete Systems**  
Shipment, stocking and storage services

### The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



**Electromechanical**  
Electromechanical actuators, motors, controllers & drivers



**Pneumatics**  
Pneumatic linear and rotary actuators, valves, and air supply



**PLCs and I/O Devices**  
PLC's, operator interfaces, sensors and I/O devices

### Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 16,000 employees in 60 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

### Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.




© Copyright 2013, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmental friendly printing plant.

# Festo North America



**1 Festo Canada  
Headquarters  
Festo Inc.**  
5300 Explorer Drive  
Mississauga, ON  
L4W 5G4

**2 Montréal**  
5600, Trans-Canada  
Pointe-Claire, QC  
H9R 1B6

**3 Québec City**  
2930, rue Watt#117  
Québec, QC  
G1X 4G3



**4 Festo United States  
Headquarters  
Festo Corporation**  
395 Moreland Road  
Hauppauge, NY  
11788

**5 Appleton**  
North 922 Tower View Drive, Suite N  
Greenville, WI  
54942

**7 Detroit**  
1441 West Long Lake Road  
Troy, MI  
48098

**6 Chicago**  
85 W Algonquin - Suite 340  
Arlington Heights, IL  
60005

**8 Silicon Valley**  
4935 Southfront Road, Suite F  
Livermore, CA  
94550

## Festo Regional Contact Center

### Canadian Customers

Commercial Support:  
Tel: 1 877 GO FESTO (1 877 463 3786)  
Fax: 1 877 FX FESTO (1 877 393 3786)  
Email: festo.canada@ca.festo.com

Technical Support:  
Tel: 1 866 GO FESTO (1 866 463 3786)  
Fax: 1 877 FX FESTO (1 877 393 3786)  
Email: technical.support@ca.festo.com

### USA Customers

Commercial Support:  
Tel: 1 800 99 FESTO (1 800 993 3786)  
Fax: 1 800 96 FESTO (1 800 963 3786)  
Email: customer.service@us.festo.com

Technical Support:  
Tel: 1 866 GO FESTO (1 866 463 3786)  
Fax: 1 800 96 FESTO (1 800 963 3786)  
Email: product.support@us.festo.com