


Compact cylinders DMM/EMM, Multimount



# Compact cylinders DMM/EMM, Multimount



Product range overview

Function	Version	Type	Piston Ø [mm]	Stroke [mm]	Position sensing	
Double-acting	<b>Basic version</b>					
		DMM Piston rod at one end	10	5, 10, 15, 20, 25, 30	■	
			16	5, 10, 15, 20, 25, 30, 40		
			20, 25, 32	5, 10, 15, 20, 25, 30, 40, 50		
		DMM-...-S2 Through piston rod	10	5, 10, 15, 20, 25, 30	■	
			16	5, 10, 15, 20, 25, 30, 40		
			20, 25, 32	5, 10, 15, 20, 25, 30, 40, 50		
		DMM-...-S20 Through, hollow piston rod	16	5, 10, 15, 20, 25, 30, 40	■	
			20, 25, 32	5, 10, 15, 20, 25, 30, 40, 50		
	Double-acting	<b>Non-rotating version</b>				
			DMML Piston rod at one end	10	5, 10, 15, 20, 25, 30	■
				16	5, 10, 15, 20, 25, 30, 40	
20, 25, 32				5, 10, 15, 20, 25, 30, 40, 50		
		DMML-...-S2 Through piston rod	10	5, 10, 15, 20, 25, 30	■	
			16	5, 10, 15, 20, 25, 30, 40		
			20, 25, 32	5, 10, 15, 20, 25, 30, 40, 50		
		DMML-...-S20 Through, hollow piston rod	16	5, 10, 15, 20, 25, 30, 40	■	
			20, 25, 32	5, 10, 15, 20, 25, 30, 40, 50		
Single-acting		<b>Basic version</b>				
			EMM Piston rod at one end, pushing	10, 16, 20, 25, 32	5, 10, 15	■
				10, 16, 20, 25, 32	5, 10, 15	
		EMMZ Piston rod at one end, pulling	10, 16, 20, 25, 32	5, 10, 15	■	
			10, 16, 20, 25, 32	5, 10, 15		
	Single-acting	<b>Non-rotating version</b>				
		EMML Piston rod at one end, pushing	10, 16, 20, 25, 32	5, 10, 15	■	
			10, 16, 20, 25, 32	5, 10, 15		
	EMMLZ Piston rod at one end, pulling	10, 16, 20, 25, 32	5, 10, 15	■		

# Compact cylinders DMM/EMM, Multimount


Product range overview

Type	Piston rod with male thread	S6 Heat resistant up to 120 °C	→ Page/Internet
<b>Basic version</b>			
<b>DMM</b> Piston rod at one end	■	■	7
<b>DMM-...-S2</b> Through piston rod	■	-	7
<b>DMM-...-S20</b> Through, hollow piston rod	■	-	7
<b>Non-rotating version</b>			
<b>DMML</b> Piston rod at one end	■	■	7
<b>DMML-...-S2</b> Through piston rod	■	-	7
<b>DMML-...-S20</b> Through, hollow piston rod	■	-	7
<b>Basic version</b>			
<b>EMM</b> Piston rod at one end, pushing	■	■	13
<b>EMMZ</b> Piston rod at one end, pulling	■	■	13
<b>Non-rotating version</b>			
<b>EMML</b> Piston rod at one end, pushing	■	■	13
<b>EMMLZ</b> Piston rod at one end, pulling	■	■	13

# Compact cylinders DMM/EMM, Multimount

Peripherals overview

FESTO











## Variants

**DMM**  
DMM-...-S2, DMM-...-S20

**DMML**  
DMML-...-S2, DMML-...-S20

**EMM**  
EMMZ

**EMML**  
EMMLZ




# Compact cylinders DMM/EMM, Multimount

Peripherals overview


Accessories						
	Brief description	DMM DMM-...-S2 DMM-...-S20	DMML DMML-...-S2 DMML-...-S20	EMM EMMZ	EMML EMMLZ	→ Page/Internet
1	Rod eye SGS	■	■	■	■	18
2	Rod clevis SG	■	■	■	■	18
3	Self-aligning rod coupler FK	■	■	■	■	18
4	Adapter AD	■ S20	■ S20	-	-	18
5	Proximity sensor SME/SMT-8	■	■	■	■	18
6	One-way flow control valve GRLA/GRLZ	■	■	■	■	19
7	Push-in connector QS	■	■	■	■	quick star

## Mounting options


Mounting at front




Mounting at rear



Vertical mounting



Horizontal mounting



# Compact cylinders DMM/EMM, Multimount

Type code


DMML – 25 – 30 – P – A – S2

Type	
Double-acting	
DMM	Basic version
DMML	Non-rotating version
Single-acting	
EMM	Basic version
EMMZ	Basic version, pulling
EMML	Non-rotating version
EMMLZ	Non-rotating version, pulling
Piston Ø [mm]	
Stroke [mm]	
Cushioning	
P	Flexible cushioning rings/plates at both ends
Position sensing	
A	For proximity sensing
Variant	
S2	Through piston rod
S6	Heat resistant up to 120 °C
S20	Through, hollow piston rod

# Compact cylinders DMM, Multimount

Technical data


Function





- N- Diameter  
10 ... 32 mm
- T- Stroke length  
5 ... 50 mm

www.festo.com/en/  
Spare\_parts\_service

Variants



S2  
S6  
S20



General technical data					
Piston Ø	10	16	20	25	32
Pneumatic connection	M3	M5	M5	M5	G1/8
End of piston rod Male thread	M4	M6	M8	M10x1.25	M10x1.25
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]				
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)				
Max. operating pressure [bar]	10				
Constructional design	Piston				
	Piston rod				
Cushioning	Flexible cushioning rings/plates at both ends				
Position sensing	For proximity sensing				
Type of mounting	Via through holes				
	Via female thread				
Mounting position	Any				

Ambient conditions		
Variant	Basic version	S6
Ambient temperature <sup>1)</sup> [°C]	-20 ... +80	0 ... +120

1) Note operating range of proximity sensors

# Compact cylinders DMM, Multimount

Technical data


Forces [N] and impact energy [J]					
Piston $\varnothing$	10	16	20	25	32
Theoretical force at 6 bar, advancing		47	121	188	295
	S2/S20	40	104	158	247
Theoretical force at 6 bar, retracting		40	104	158	247
	S2/S20	40	104	158	247
Max. impact energy at end positions	0.1	0.2	0.3	0.6	0.6

Technical data – Protection against rotation					
Piston $\varnothing$	10	16	20	25	32
Max. torque at the piston rod <sup>1)</sup> [Nm]	0.02	0.01	0.01	0.015	0.02

1) The max. torque must not be exceeded even when fitting attachments.

## Materials

Sectional view



Compact cylinder	Basic version	S6
1 Housing	Wrought aluminium alloy	Wrought aluminium alloy
2 Plug cap	Brass	Brass
3 Piston rod	High-alloy stainless steel	High-alloy stainless steel
- Seals	Polyurethane	Fluorocarbon rubber



# Compact cylinders DMM, Multimount


Technical data

FESTO


## Dimensions – Basic cylinder

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

### Basic version DMM



### Non-rotating version DMML



∅	AM	B3	BG	D1	D2	D5	D6	E	EE	H2	H3	H4	H5	KK	L1	L2
[mm]			+0.5	∅	∅ H7	∅ +0.2	∅ +0.3									
10	12	14	5	–	10.8	3.4	6	15	M3	13	9	11	19.5	M4	0.9	48
16	16	15	6	12.9	17	4.3	7.5	20	M5	19	13	15.5	24	M6	0.9	52
20	20	15	7.5	16	21	5.5	10	26	M5	24	16	19.5	29	M8	1.9	55
25	22	18	7.5	20	26	5.5	10	32	M5	30	20	24.5	36	M10x1.25	1.9	58
32	22	20	9	26	33	6.6	11	40	G <sup>1</sup> / <sub>8</sub>	40	24	30.5	45	M10x1.25	1.9	62

∅	L3	L4	L5	L6	MM	PJ	PL	RT	T1	UO	TO	WH	ZJ	≈C1	Max. tightening torque
[mm]					∅									h13	[Nm] +10%
10	11	57	9	–	4	12	24	M3	5	25	19	2	50	–	1
16	13.5	64	12	3	6	16.5	22	M4	5.5	32	27	5	57	5	2.5
20	16	68	13	4	8	16.8	25.7	M5	8	40	33	6	61	7	3
25	17	72	14	5	10	18.5	24.7	M5	9	50	41	7	65	9	8
32	19	77	15	6	12	19	26	M6	11.5	62	52	8	70	10	9

# Compact cylinders DMM, Multimount

Technical data

FESTO



## Dimensions – Variants

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

S2 – Through piston rod

Basic version DMM

Non-rotating version DMML





- + = plus stroke length
- ++ = plus 2x stroke length

S20 – Through, hollow piston rod

Basic version DMM

Non-rotating version DMML




- + = plus stroke length
- ++ = plus 2x stroke length

∅	D8	L4	L8	ZJ	ZM
[mm]	∅				
10	–	57	59	50	52
16	2.3	64	69	57	62
20	3.2	68	74	61	67
25	3.8	72	79	65	72
32	4.5	77	85	70	78

# Compact cylinders DMM, Multimount

Technical data

FESTO

Ordering data – Basic cylinder						
Type	Piston Ø [mm]	Stroke <sup>1)</sup> [mm]	Basic version DMM		Non-rotating version DMML	
			Part No.	Type	Part No.	Type
	10	5	158 502	DMM-10-5-P-A	158 557	DMML-10-5-P-A
		10	158 503	DMM-10-10-P-A	158 558	DMML-10-10-P-A
		15	158 504	DMM-10-15-P-A	158 559	DMML-10-15-P-A
		20	158 505	DMM-10-20-P-A	158 560	DMML-10-20-P-A
		25	158 506	DMM-10-25-P-A	158 561	DMML-10-25-P-A
		30	158 507	DMM-10-30-P-A	158 562	DMML-10-30-P-A
		16	5	158 511	DMM-16-5-P-A	158 566
	10		158 512	DMM-16-10-P-A	158 567	DMML-16-10-P-A
	15		158 513	DMM-16-15-P-A	158 568	DMML-16-15-P-A
	20		158 514	DMM-16-20-P-A	158 569	DMML-16-20-P-A
	25		158 515	DMM-16-25-P-A	158 570	DMML-16-25-P-A
	30		158 516	DMM-16-30-P-A	158 571	DMML-16-30-P-A
	40		178 210	DMM-16-40-P-A	178 328	DMML-16-40-P-A
	20	5	158 521	DMM-20-5-P-A	158 576	DMML-20-5-P-A
		10	158 522	DMM-20-10-P-A	158 577	DMML-20-10-P-A
		15	158 523	DMM-20-15-P-A	158 578	DMML-20-15-P-A
		20	158 524	DMM-20-20-P-A	158 579	DMML-20-20-P-A
		25	158 525	DMM-20-25-P-A	158 580	DMML-20-25-P-A
		30	158 526	DMM-20-30-P-A	158 581	DMML-20-30-P-A
		40	158 527	DMM-20-40-P-A	158 582	DMML-20-40-P-A
		50	158 528	DMM-20-50-P-A	158 583	DMML-20-50-P-A
		25	5	158 533	DMM-25-5-P-A <sup>2)</sup>	158 588
	10		158 534	DMM-25-10-P-A <sup>2)</sup>	158 589	DMML-25-10-P-A <sup>2)</sup>
	15		158 535	DMM-25-15-P-A <sup>2)</sup>	158 590	DMML-25-15-P-A <sup>2)</sup>
	20		158 536	DMM-25-20-P-A <sup>2)</sup>	158 591	DMML-25-20-P-A <sup>2)</sup>
	25		158 537	DMM-25-25-P-A <sup>2)</sup>	158 592	DMML-25-25-P-A <sup>2)</sup>
	30		158 538	DMM-25-30-P-A <sup>2)</sup>	158 593	DMML-25-30-P-A <sup>2)</sup>
	40		158 539	DMM-25-40-P-A <sup>2)</sup>	158 594	DMML-25-40-P-A <sup>2)</sup>
50	158 540		DMM-25-50-P-A <sup>2)</sup>	158 595	DMML-25-50-P-A <sup>2)</sup>	
32	5	158 545	DMM-32-5-P-A <sup>2)</sup>	158 600	DMML-32-5-P-A <sup>2)</sup>	
	10	158 546	DMM-32-10-P-A <sup>2)</sup>	158 601	DMML-32-10-P-A <sup>2)</sup>	
	15	158 547	DMM-32-15-P-A <sup>2)</sup>	158 602	DMML-32-15-P-A <sup>2)</sup>	
	20	158 548	DMM-32-20-P-A <sup>2)</sup>	158 603	DMML-32-20-P-A <sup>2)</sup>	
	25	158 549	DMM-32-25-P-A <sup>2)</sup>	158 604	DMML-32-25-P-A <sup>2)</sup>	
	30	158 550	DMM-32-30-P-A <sup>2)</sup>	158 605	DMML-32-30-P-A <sup>2)</sup>	
	40	158 551	DMM-32-40-P-A <sup>2)</sup>	158 606	DMML-32-40-P-A <sup>2)</sup>	
	50	158 552	DMM-32-50-P-A <sup>2)</sup>	158 607	DMML-32-50-P-A <sup>2)</sup>	




1) Additional stroke lengths upon request

2) The scope of delivery includes a hexagonal nut for the piston rod thread

# Compact cylinders DMM, Multimount

Technical data

FESTO

Ordering data – Variants						
Type	Piston Ø [mm]	Stroke <sup>1)</sup> [mm]	Basic version DMM		Non-rotating version DMML	
			Part No.	Type	Part No.	Type
<b>S2 – Through piston rod</b>						
	10	5, 10, 20, 25, 30	<b>158 508</b>	<b>DMM-10-...-P-A-S2</b>	<b>158 563</b>	<b>DMML-10-...-P-A-S2</b>
	16	5, 10, 15, 20, 25, 30, 40	<b>158 517</b>	<b>DMM-16-...-P-A-S2</b>	<b>158 572</b>	<b>DMML-16-...-P-A-S2</b>
	20	5, 10, 15, 20, 25, 30, 40, 50	<b>158 529</b>	<b>DMM-20-...-P-A-S2</b>	<b>158 584</b>	<b>DMML-20-...-P-A-S2</b>
	25	5, 10, 15, 20, 25, 30, 40, 50	<b>158 541</b>	<b>DMM-25-...-P-A-S2<sup>2)</sup></b>	<b>158 596</b>	<b>DMML-25-...-P-A-S2<sup>2)</sup></b>
	32	5, 10, 15, 20, 25, 30, 40, 50	<b>158 553</b>	<b>DMM-32-...-P-A-S2<sup>2)</sup></b>	<b>158 608</b>	<b>DMML-32-...-P-A-S2<sup>2)</sup></b>
<b>S6 – Heat resistant up to 120 °C</b>						
	10	5, 10, 15, 20, 25, 30	<b>158 509</b>	<b>DMM-10-...-P-A-S6</b>	<b>158 564</b>	<b>DMML-10-...-P-A-S6</b>
	16	5, 10, 15, 20, 25, 30, 40	<b>158 518</b>	<b>DMM-16-...-P-A-S6</b>	<b>158 573</b>	<b>DMML-16-...-P-A-S6</b>
	20	5, 10, 15, 20, 25, 30, 40, 50	<b>158 530</b>	<b>DMM-20-...-P-A-S6</b>	<b>158 585</b>	<b>DMML-20-...-P-A-S6</b>
	25	5, 10, 15, 20, 25, 30, 40, 50	<b>158 542</b>	<b>DMM-25-...-P-A-S6<sup>2)</sup></b>	<b>158 597</b>	<b>DMML-25-...-P-A-S6<sup>2)</sup></b>
	32	5, 10, 15, 20, 25, 30, 40, 50	<b>158 554</b>	<b>DMM-32-...-P-A-S6<sup>2)</sup></b>	<b>158 609</b>	<b>DMML-32-...-P-A-S6<sup>2)</sup></b>
<b>S20 – Through, hollow piston rod</b>						
	16	5, 10, 15, 20, 25, 30, 40	<b>158 519</b>	<b>DMM-16-...-P-A-S20</b>	<b>158 574</b>	<b>DMML-16-...-P-A-S20</b>
	20	5, 10, 15, 20, 25, 30, 40, 50	<b>158 531</b>	<b>DMM-20-...-P-A-S20</b>	<b>158 586</b>	<b>DMML-20-...-P-A-S20</b>
	25	5, 10, 15, 20, 25, 30, 40, 50	<b>158 543</b>	<b>DMM-25-...-P-A-S20<sup>2)</sup></b>	<b>158 598</b>	<b>DMML-25-...-P-A-S20<sup>2)</sup></b>
	32	5, 10, 15, 20, 25, 30, 40, 50	<b>158 555</b>	<b>DMM-32-...-P-A-S20<sup>2)</sup></b>	<b>158 610</b>	<b>DMML-32-...-P-A-S20<sup>2)</sup></b>

1) Additional stroke lengths upon request

2) The scope of delivery includes a hexagonal nut for the piston rod thread

# Compact cylinders EMM, Multimount


Technical data

Function

**EMM, EMLL**




**EMMZ, EMLLZ**



Variants




S6



EMM-...-P-A

EMLL-...-P-A



EMMZ-...-P-A

EMLLZ-...-P-A

- N- Diameter  
10 ... 32 mm
- T- Stroke length  
5 ... 15 mm

www.festo.com/en/  
Spare\_parts\_service

General technical data					
Piston Ø	10	16	20	25	32
Pneumatic connection	M3	M5	M5	M5	G1/8
End of piston rod Male thread	M4	M6	M8	M10x1.25	M10x1.25
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]				
Note on operating/ pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)				
Max. operating pressure [bar]	10				
Max. applied load <sup>1)</sup> [g]	40	120	160	260	320
Constructional design	Piston				
	Piston rod				
Cushioning	Flexible cushioning rings/plates at both ends				
Position sensing	For proximity sensing				
Type of mounting	Via through holes				
	Via female thread				
Mounting position	Any				

1) At 6 bar. For other values see graph "Maximum permissible impact velocity v as a function of the applied load m" → 14

Ambient conditions		
Variant	Basic version	S6
Ambient temperature <sup>1)</sup> [°C]	-20 ... +80	0 ... +120

1) Note operating range of proximity sensors


# Compact cylinders EMM, Multimount

Technical data


FESTO

Forces [N] and impact energy [J]						
Piston $\varnothing$		10	16	20	25	32
Theoretical force at 6 bar, advancing	EMM/EM ML	37	101	165	227	456
	EMMZ/E MMLZ	30	84	135	179	388
Max. impact energy at end positions		0.1	0.2	0.3	0.6	0.6

## Maximum permissible impact velocity $v$ as a function of the applied load $m$      Minimum spring return force $F$ as a function of the stroke $l$



- 1  $\varnothing$  10 mm
- 2  $\varnothing$  16 mm
- 3  $\varnothing$  20 mm
- 4  $\varnothing$  25 mm



- 5  $\varnothing$  32 mm



Technical data – Protection against rotation						
Piston $\varnothing$		10	16	20	25	32
Max. torque at the piston rod <sup>1)</sup> [Nm]		0.02	0.01	0.01	0.015	0.02

1) The max. torque must not be exceeded even when fitting attachments

## Materials

Sectional view EMM(L) – Pushing

Sectional view EMM(L)Z – Pulling



Compact cylinder	Basic version	S6
1 Housing	Wrought aluminium alloy	Wrought aluminium alloy
2 Plug cap	Brass	Brass
3 Piston rod	High-alloy stainless steel	High-alloy stainless steel
– Seals	Polyurethane	Fluorocarbon rubber

# Compact cylinders EMM, Multimount


Technical data

FESTO


## Dimensions

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

### Basic version EMM – Pushing



### Non-rotating version EMML – Pushing



∅	AM	B3	BG	D1	D2	D5	D6	E	EE	H2	H3	H4	H5	KK	L1	L2
[mm]			+0.5	∅	∅ H7	∅ +0.2	∅ +0.3									
10	12	14	5	–	10.8	3.4	6	15	M3	13	9	11	19.5	M4	0.9	48
16	16	15	6	12.9	17	4.3	7.5	20	M5	19	13	15.5	24	M6	0.9	52
20	20	15	7.5	16	21	5.5	10	26	M5	24	16	19.5	29	M8	1.9	55
25	22	18	7.5	20	26	5.5	10	32	M5	30	20	24.5	36	M10x1.25	1.9	58
32	22	20	9	26	33	6.6	11	40	G <sup>1</sup> / <sub>8</sub>	40	24	30.5	45	M10x1.25	1.9	62

∅	L3	L4	L5	L6	MM	PJ	PL	RT	T1	U0	T0	WH	ZJ	∅C1	Max. tightening torque
[mm]					∅									h13	[Nm] +10%
10	11	57	9	–	4	12	24	M3	5	25	19	2	50	–	1
16	13.5	64	12	3	6	16.5	22	M4	5.5	32	27	5	57	5	2.5
20	16	68	13	4	8	16.8	25.7	M5	8	40	33	6	61	7	3
25	17	72	14	5	10	18.5	24.7	M5	9	50	41	7	65	9	8
32	19	77	15	6	12	19	26	M6	11.5	62	52	8	70	10	9


# Compact cylinders EMM, Multimount

Technical data


FESTO

Download CAD Data → [www.festo.com/us/cad](http://www.festo.com/us/cad)

**Basic version EMMZ – Pulling**




**Non-rotating version EMMLZ – Pulling**



+ = plus stroke length  
++ = plus 2x stroke length

∅	L4	L5	WH	ZJ
[mm]				
10	57	9	2	50
16	64	12	5	57
20	68	13	6	61
25	72	14	7	65
32	77	15	8	70

Ordering data – Basic cylinder, pushing						
Type	Piston ∅ [mm]	Stroke <sup>1)</sup> [mm]	Basic version EMM		Non-rotating version EMML	
			Part No.	Type	Part No.	Type
	10	5	158 612	EMM-10-5-P-A	158 637	EMML-10-5-P-A
		10	158 613	EMM-10-10-P-A	158 638	EMML-10-10-P-A
		15	158 614	EMM-10-15-P-A	158 639	EMML-10-15-P-A
	16	5	158 617	EMM-16-5-P-A	158 642	EMML-16-5-P-A
		10	158 618	EMM-16-10-P-A	158 643	EMML-16-10-P-A
		15	158 619	EMM-16-15-P-A	158 644	EMML-16-15-P-A
	20	5	158 622	EMM-20-5-P-A	158 647	EMML-20-5-P-A
		10	158 623	EMM-20-10-P-A	158 648	EMML-20-10-P-A
		15	158 624	EMM-20-15-P-A	158 649	EMML-20-15-P-A
	25	5	158 627	EMM-25-5-P-A <sup>2)</sup>	158 652	EMML-25-5-P-A <sup>2)</sup>
		10	158 628	EMM-25-10-P-A <sup>2)</sup>	158 653	EMML-25-10-P-A <sup>2)</sup>
		15	158 629	EMM-25-15-P-A <sup>2)</sup>	158 654	EMML-25-15-P-A <sup>2)</sup>
32	5	158 632	EMM-32-5-P-A <sup>2)</sup>	158 657	EMML-32-5-P-A <sup>2)</sup>	
	10	158 633	EMM-32-10-P-A <sup>2)</sup>	158 658	EMML-32-10-P-A <sup>2)</sup>	
	15	158 634	EMM-32-15-P-A <sup>2)</sup>	158 659	EMML-32-15-P-A <sup>2)</sup>	


- 1) Additional stroke lengths upon request  
2) The scope of delivery includes a hexagonal nut for the piston rod thread




# Compact cylinders EMM, Multimount

Technical data


FESTO

Ordering data – Basic cylinder, pulling						
Type	Piston Ø [mm]	Stroke <sup>1)</sup> [mm]	Basic version EMMZ		Non-rotating version EMMLZ	
			Part No.	Type	Part No.	Type
	10	5	158 662	EMMZ-10-5-P-A	158 687	EMMLZ-10-5-P-A
		10	158 663	EMMZ-10-10-P-A	158 688	EMMLZ-10-10-P-A
		15	158 664	EMMZ-10-15-P-A	158 689	EMMLZ-10-15-P-A
	16	5	158 667	EMMZ-16-5-P-A	158 692	EMMLZ-16-5-P-A
		10	158 668	EMMZ-16-10-P-A	158 693	EMMLZ-16-10-P-A
		15	158 669	EMMZ-16-15-P-A	158 694	EMMLZ-16-15-P-A
	20	5	158 672	EMMZ-20-5-P-A	158 697	EMMLZ-20-5-P-A
		10	158 673	EMMZ-20-10-P-A	158 698	EMMLZ-20-10-P-A
		15	158 674	EMMZ-20-15-P-A	158 699	EMMLZ-20-15-P-A
	25	5	158 677	EMMZ-25-5-P-A <sup>2)</sup>	158 702	EMMLZ-25-5-P-A <sup>2)</sup>
		10	158 678	EMMZ-25-10-P-A <sup>2)</sup>	158 703	EMMLZ-25-10-P-A <sup>2)</sup>
		15	158 679	EMMZ-25-15-P-A <sup>2)</sup>	158 704	EMMLZ-25-15-P-A <sup>2)</sup>
	32	5	158 682	EMMZ-32-5-P-A <sup>2)</sup>	158 707	EMMLZ-32-5-P-A <sup>2)</sup>
		10	158 683	EMMZ-32-10-P-A <sup>2)</sup>	158 708	EMMLZ-32-10-P-A <sup>2)</sup>
		15	158 684	EMMZ-32-15-P-A <sup>2)</sup>	158 709	EMMLZ-32-15-P-A <sup>2)</sup>

- 1) Additional stroke lengths upon request
- 2) The scope of delivery includes a hexagonal nut for the piston rod thread

Ordering data – Pushing variants						
Type	Piston Ø [mm]	Stroke <sup>1)</sup> [mm]	Basic version EMM		Non-rotating version EMML	
			Part No.	Type	Part No.	Type
S6 – Heat resistant up to 120 °C						
	10	5, 10, 15	158 615	EMM-10-...-P-A-S6	158 640	EMML-10-...-P-A-S6
	16	5, 10, 15	158 620	EMM-16-...-P-A-S6	158 645	EMML-16-...-P-A-S6
	20	5, 10, 15	158 625	EMM-20-...-P-A-S6	158 650	EMML-20-...-P-A-S6
	25	5, 10, 15	158 630	EMM-25-...-P-A-S6 <sup>2)</sup>	158 655	EMML-25-...-P-A-S6 <sup>2)</sup>
	32	5, 10, 15	158 635	EMM-32-...-P-A-S6 <sup>2)</sup>	158 660	EMML-32-...-P-A-S6 <sup>2)</sup>

- 1) Additional stroke lengths upon request
- 2) The scope of delivery includes a hexagonal nut for the piston rod thread





Ordering data – Pulling variants						
Type	Piston Ø [mm]	Stroke <sup>1)</sup> [mm]	Basic version EMMZ		Non-rotating version EMMLZ	
			Part No.	Type	Part No.	Type
S6 – Heat resistant up to 120 °C						
	10	5, 10, 15	158 665	EMMZ-10-...-P-A-S6	158 690	EMMLZ-10-...-P-A-S6
	16	5, 10, 15	158 670	EMMZ-16-...-P-A-S6	158 695	EMMLZ-16-...-P-A-S6
	20	5, 10, 15	158 675	EMMZ-20-...-P-A-S6	158 700	EMMLZ-20-...-P-A-S6
	25	5, 10, 15	158 680	EMMZ-25-...-P-A-S6 <sup>2)</sup>	158 705	EMMLZ-25-...-P-A-S6 <sup>2)</sup>
	32	5, 10, 15	158 685	EMMZ-32-...-P-A-S6 <sup>2)</sup>	158 710	EMMLZ-32-...-P-A-S6 <sup>2)</sup>



- 1) Additional stroke lengths upon request
- 2) The scope of delivery includes a hexagonal nut for the piston rod thread

# Compact cylinders DMM/EMM, Multimount

Accessories

FESTO




Ordering data – Piston rod attachments				Technical data → Internet: piston-rod attachment			
Designation	For Ø	Part No.	Type	Designation	For Ø	Part No.	Type
<b>Rod eye SGS</b>				<b>Self-aligning rod coupler FK</b>			
	10	9 253	SGS-M4		10	6 528	FK-M4
	16	9 254	SGS-M6		16	2 061	FK-M6
	20	9 255	SGS-M8		20	2 062	FK-M8
	25	9 261	SGS-M10x1,25		25	6 140	FK-M10x1,25
	32				32		
<b>Rod clevis SG</b>				<b>Adapter AD</b>			
	10	6 532	SG-M4		16	157 328	AD-M6-M5
	16	3 110	SG-M6			157 329	AD-M6-1/8
	20	3 111	SG-M8			157 330	AD-M6-1/4
	25	6 144	SG-M10x1,25		20	157 331	AD-M8-1/8
	32					157 332	AD-M8-1/4
				25	157 333	AD-M10x1,25-1/8	
				32	157 334	AD-M10x1,25-1/4	



Ordering data – Proximity sensors for T-slot, magneto-resistive					Technical data → Internet: smt	
	Type of mounting	Switch output	Electrical connection	Cable length [m]	Part No.	Type
<b>N/O contact</b>						
	Insertable in the slot from above, flush with cylinder profile, short design	PNP	Cable, 3-wire	2.5	574335	SMT-8M-A-PS-24V-E-2,5-OE
			Plug M8x1, 3-pin	0.3	574334	SMT-8M-A-PS-24V-E-0,3-M8D
			Plug M12x1, 3-pin	0.3	574337	SMT-8M-A-PS-24V-E-0,3-M12
		NPN	Cable, 3-wire	2.5	574338	SMT-8M-A-NS-24V-E-2,5-OE
			Plug M8x1, 3-pin	0.3	574339	SMT-8M-A-NS-24V-E-0,3-M8D
<b>N/C contact</b>						
	Insertable in the slot from above, flush with cylinder profile, short design	PNP	Cable, 3-wire	7.5	574340	SMT-8M-A-PO-24V-E-7,5-OE



# Compact cylinders DMM/EMM, Multimount

Accessories

**FESTO**

Ordering data – Proximity sensors for T-slot, magnetic reed						Technical data → Internet: sme	
	Type of mounting	Switch output	Electrical connection	Cable length [m]	Part No.	Type	
<b>N/O contact</b>							
	Insertable in the slot from above, flush with cylinder profile	Contacting	Cable, 3-wire	2.5	543 862	SME-8M-DS-24V-K-2,5-OE	
				5.0	543 863	SME-8M-DS-24V-K-5,0-OE	
			Plug M8x1, 3-pin	2.5	543 872	SME-8M-ZS-24V-K-2,5-OE	
				0.3	543 861	SME-8M-DS-24V-K-0,3-M8D	
	Insertable in the slot lengthwise, flush with the cylinder profile	Contacting	Cable, 3-wire	2.5	150 855	SME-8-K-LED-24	
				0.3	150 857	SME-8-S-LED-24	
<b>N/C contact</b>							
	Insertable in the slot lengthwise, flush with the cylinder profile	Contacting	Cable, 3-wire	7.5	160 251	SME-8-O-K-LED-24	

Ordering data – Connecting cables					Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type	
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 333	NEBU-M8G3-K-2.5-LE3	
			5	541 334	NEBU-M8G3-K-5-LE3	
	Straight socket, M12x1, 5-pin	Cable, open end, 3-wire	2.5	541 363	NEBU-M12G5-K-2.5-LE3	
			5	541 364	NEBU-M12G5-K-5-LE3	
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 338	NEBU-M8W3-K-2.5-LE3	
			5	541 341	NEBU-M8W3-K-5-LE3	
	Angled socket, M12x1, 5-pin	Cable, open end, 3-wire	2.5	541 367	NEBU-M12W5-K-2.5-LE3	
			5	541 370	NEBU-M12W5-K-5-LE3	

Ordering data – One-way flow control valves					Technical data → Internet: grl				
	Connection		Material	Part No.	Type				
	Thread	For tubing OD							
<b>For exhaust air</b>									
	M3	3	Metal design	175 041	GRLA-M3-QS-3				
		M5		3	193 137	GRLA-M5-QS-3-D			
				4	193 138	GRLA-M5-QS-4-D			
				6	193 139	GRLA-M5-QS-6-D			
	G1/8	3		193 142	GRLA-1/8-QS-3-D				
		4		193 143	GRLA-1/8-QS-4-D				
		6		193 144	GRLA-1/8-QS-6-D				
		8		193 145	GRLA-1/8-QS-8-D				
		<b>For supply air</b>							
				M3	3	Metal design	175 043	GRLZ-M3-QS-3	
M5	3		193 153		GRLZ-M5-QS-3-D				
	4		193 154		GRLZ-M5-QS-4-D				
	6		193 155		GRLZ-M5-QS-6-D				
G1/8	3		193 156	GRLZ-1/8-QS-3-D					
	4		193 157	GRLZ-1/8-QS-4-D					
	6		193 158	GRLZ-1/8-QS-6-D					
	8		193 159	GRLZ-1/8-QS-8-D					

# Product Range and Company Overview

## A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



**Custom Automation Components**  
Complete custom engineered solutions



**Custom Control Cabinets**  
Comprehensive engineering support and on-site services



**Complete Systems**  
Shipment, stocking and storage services

## The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



**Electromechanical**  
Electromechanical actuators, motors, controllers & drives



**Pneumatics**  
Pneumatic linear and rotary actuators, valves, and air supply



**PLCs and I/O Devices**  
PLC's, operator interfaces, sensors and I/O devices

## Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

## Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

# Festo North America

## Festo Regional Contact Center

5300 Explorer Drive  
Mississauga, Ontario L4W 5G4  
Canada

### USA Customers:

For ordering assistance,

**Call:** 1.800.99.FESTO (1.800.993.3786)

**Fax:** 1.800.96.FESTO (1.800.963.3786)

**Email:** [customer.service@us.festo.com](mailto:customer.service@us.festo.com)

For technical support,

**Call:** 1.866.GO.FESTO (1.866.463.3786)

**Fax:** 1.800.96.FESTO (1.800.963.3786)

**Email:** [product.support@us.festo.com](mailto:product.support@us.festo.com)

### Canadian Customers:

**Call:** 1.877.GO.FESTO (1.877.463.3786)

**Fax:** 1.877.FX.FESTO (1.877.393.3786)

**Email:** [festo.canada@ca.festo.com](mailto:festo.canada@ca.festo.com)

---

## USA Headquarters

Festo Corporation  
395 Moreland Road  
P.O. Box 18023  
Hauppauge, NY 11788, USA  
[www.festo.com/us](http://www.festo.com/us)

---

## USA Sales Offices

### Appleton

North 922 Tower View Drive, Suite N  
Greenville, WI 54942, USA

### Boston

120 Presidential Way, Suite 330  
Woburn, MA 01801, USA

### Chicago

1441 East Business Center Drive  
Mt. Prospect, IL 60056, USA

### Dallas

1825 Lakeway Drive, Suite 600  
Lewisville, TX 75057, USA

### Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320  
Auburn Hills, MI 48326, USA

### New York

395 Moreland Road  
Hauppauge, NY 11788, USA

### Silicon Valley

4935 Southfront Road, Suite F  
Livermore, CA 94550, USA

## United States



**USA Headquarters, East:** Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: [info@festo-usa.com](mailto:info@festo-usa.com)

[www.festo.com/us](http://www.festo.com/us)

## Canada



**Headquarters:** Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: [festo.canada@ca.festo.com](mailto:festo.canada@ca.festo.com)

[www.festo.ca](http://www.festo.ca)

## Mexico



**Headquarters:** Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,  
54020 Tlalneantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: [festo.mexico@mx.festo.com](mailto:festo.mexico@mx.festo.com)

[www.festo.com/mx](http://www.festo.com/mx)

---

## Central USA

Festo Corporation  
1441 East Business  
Center Drive  
Mt. Prospect, IL 60056, USA  
Phone: 1.847.759.2600  
Fax: 1.847.768.9480



## Western USA

Festo Corporation  
4935 Southfront Road,  
Suite F  
Livermore, CA 94550, USA  
Phone: 1.925.371.1099  
Fax: 1.925.245.1286



---

## Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark  
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia  
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore  
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

[www.festo.com](http://www.festo.com)