

Linear modules HMP



Linear modules HMP

Key features


FESTO

At a glance

 New

- Sturdier
- Optimised end stop system
- Optimised intermediate position module
- Minimised susceptibility to wear
- One-way flow control valves that can be externally adjusted
- Integrated sensor strip

- Diameters of 16 ... 32 mm
- Stroke lengths of 50 ... 400 mm
- Extremely rigid basic profile
- Infinitely adjustable end stops
- Rotatable yoke plate
- Integrated clamping unit
- Precision backlash-free guide system
- Freely adjustable intermediate position
- Adjustable end-position cushioning
- Integrated sensors:
 - Sensor strip for proximity sensors for end-position sensing
 - Mounting slot for proximity sensors for position sensing
- Functional end cap:
 - Pneumatic interface
 - Electrical interface
- Highly flexible thanks to various mounting and assembly options:
 - Basic profile
 - Yoke plate
- Large selection of adapters for:
 - Drives
 - Grippers
- Innovative and user-friendly installation system



1 Yoke plate

Can be turned to any angle from 0 to 360°. The yoke plate cannot be turned if combined with the clamping unit. Drives and grippers can be mounted on the yoke plate by means of adapter kits (direct mounting or dovetail connections).

2 Guide system

Extremely high rigidity thanks to the hardened steel guide barrel which is supported in pre-loaded and backlash-free recirculating ball bearing guides guaranteeing the utmost precision.

3 Basic profile

Drives and basic components can be attached to the rigid light alloy profile using adapter, connector and component kits.

4 End-position cushioning

Extremely dynamic operation thanks to hydraulic shock absorbers which cushion the piston sleeve at the end positions.

5 End stop

Any desired intermediate position can be set between minimum and maximum stroke (plus the strokes of the shock absorbers).

Linear modules HMP

Key features

FESTO

Wide choice of variants

End stop

The optimised end stop system is practically wear-free. Rough adjustment is performed by moving the stop into the profile groove. Fine adjustment is performed using compressed air via a rotatable sleeve.



Clamping unit


The pneumatically-powered clamping unit can be used to hold loads at any end position and with the module installed at any angle. In the case of a pressure drop or pressure failure, the clamping unit acts like an EMERGENCY STOP device. The clamping unit can be released by means of the manual override.



End cap

Connections can be made on the top and bottom of the end cap. Pneumatic tubing and electrical cables can be bundled and routed through the end cap via conduits.


Max. 6 proximity sensors can be connected to the integral terminal strip. The switching states of the proximity sensors are indicated via a display window in the end cap.



Intermediate position module

The intermediate position module permits advancing to an additional position between the two end positions. This is done by swivelling a lever into the traversing range of the moving stop on the guide tube.












The intermediate position can be activated during the advancing stroke or retracting stroke, depending on the type of design. Multiple intermediate position modules can be installed on request.



Linear modules HMP

Key features




Mounting and assembly options			
Mounting options			
	Dovetail mounting using connecting kit HAVB 	Direct mounting using screws and slot nuts NST 	Direct mounting using screws and centring sleeves ZBH 
Mounting surfaces			
On the side of the basic profile	HMP-16/-20/-25/-32 	HMP-16/-20/-25/-32 	
On the underside of the basic profile	HMP-16/-20/-25/-32 	HMP-25/-32 	HMP-16/-20 
On the yoke plate	HMP-16/-20/-25/-32 	HMP-25/-32 	HMP-16/-20/-25/-32 

Linear modules HMP

System example

System product for handling and assembly technology




System elements and accessories		
	Brief description	→ Page/Internet
1	Drives	Wide range of combination options within handling and assembly technology drive
2	Grippers	Wide range of optional variants within handling and assembly technology gripper
3	Adapters	For drive/drive combinations 29
		For drive/gripper combinations gripper
4	Basic components	Profiles and profile combinations as well as profile/drive combinations basic component
5	Installation components	For achieving a clear-cut, safe layout of electrical cables and tubing installation component
-	Axes	Wide range of combination options within handling and assembly technology axes
-	Motors	Servo and stepper motors, with or without gearing motor

Linear modules HMP

Peripherals overview

FESTO

With clamping unit KP




Accessories			
	Brief description	→ Page/Internet	
1	Clamping unit KP	For holding loads in all mounting and end positions in the event of a drop in pressure	24
2	End cap AD/EL	The end cap (EL) houses an integrated electrical interface	24
3	Sensor strip SL	For mounting proximity sensors and flexible sensing of any desired end positions. Included in the scope of delivery of the linear module.	24
4	Centring sleeve Z	For centring loads and attachments on the yoke plate	26
5	Shock absorber	Included in the scope of delivery of the linear module	26
6	Proximity sensor A...	For position sensing via the sensor strip	27
7	Housing cover	Included in the scope of delivery of the linear module	-
-	Cable with socket V	For proximity sensor	27
-	Slot cover A	For protecting the proximity sensor cable	26

Linear modules HMP

Peripherals overview

With intermediate position module Z1A



Accessories			
	Brief description	→ Page/Internet	
1	Intermediate position module Z1A	For approaching an intermediate position during the advance stroke. The intermediate position module Z1E is used to approach an intermediate position during the return stroke.	18
2	End cap AD/EL	The end cap (EL) houses an integrated electrical interface	24
3	Sensor strip SL	For mounting proximity sensors and flexible sensing of any desired end positions. Included in the scope of delivery of the linear module.	24
4	Centring sleeve Z	For centring loads and attachments on the yoke plate	26
5	Shock absorber	Included in the scope of delivery of the linear module	26
6	Proximity sensor A...	For position sensing via the sensor strip	27
7	Housing cover	Included in the scope of delivery of the linear module	-
8	Proximity sensor A...	For sensing the position of the lever at the intermediate position module (intermediate position active/not active)	28
-	Cable with socket V	For proximity sensor	27
-	Slot cover A	For protecting the proximity sensor cable	26

Linear modules HMP

Type codes

HMP - 16 - 150 - B - SL - 2G3 - KP - - EL - A1 - E

Type

HMP	Linear module
-----	---------------

Piston Ø [mm]

Stroke [mm]

Generation

B	B series
---	----------

Sensing

SL	Sensor strip
----	--------------

Pneumatic connection

2G3	For 3 mm I.D. tubing
2G4	For 4 mm I.D. tubing
2G6	For 6 mm I.D. tubing

Clamping unit

KP	Attached
----	----------

Intermediate position module

Z1A	For advance stroke
Z1E	For return stroke

Interface

AD	End cap
EL	End cap with electrical interface

Proximity sensor


A1	With cable, 2.5 m
A2	Contactless with cable, 2.5 m, NPN
A3	Contactless with cable, 2.5 m, PNP
A4	With plug
A5	Contactless with plug, NPN
A6	Contactless with plug, PNP

User documentation

E	English
S	Spanish
F	French
I	Italian
V	Swedish
B	Express waiver – no manual to be included (already available)

Linear modules HMP

Type codes




Linear modules HMP

FESTO

Technical data


Function


Standard version



with clamping unit



-  - Piston \varnothing
16 ... 32 mm

-  - Stroke length
50 ... 400 mm

-  - www.festo.com



General technical data						
Piston \varnothing		16	20	25	32	
System mode		Yoke				
Mode of operation		Double-acting				
Protection against torsion		Guide				
Connection type		Female thread				
Pneumatic connection, linear module		M5	G $\frac{1}{8}$	G $\frac{1}{8}$	G $\frac{1}{4}$	
Pneumatic connection, intermediate position module		M3				
Assembly position		Any				
Effective stroke	[mm]	16 ... 320	24 ... 400	24 ... 400	40 ... 400	
Position sensing		For proximity sensing				
Max. repetition accuracy ¹⁾	[mm]	0.01				
Max. speed	advancing	[m/s]	0.8	1.1	1.1	1.2
	returning	[m/s]	0.8	1.1	1.1	1.1
Swivel time of lever at intermediate position module	advancing	[s]	0.04	0.04	0.04	0.072
	returning	[s]	0.04	0.036	0.034	0.065

1) Variation of end position and intermediate position for 100 successive strokes under constant operating conditions

Operating and environmental conditions					
Piston \varnothing		16	20	25	32
Operating pressure	[bar]	4 ... 8			
Operating medium		Compressed air in accordance with ISO 8573-1:2010 [7:4:4]			
Note on operating/pilot medium		Operation with lubricated medium possible (in which case lubricated operation will always be required)			
Ambient temperature ¹⁾	[°C]	0 ... +60			
Protection class to EN 60 529		IP 40			
Noise level F_{LEQ}	[dB(A)]	62	65	68	69
Corrosion resistance class CRC ²⁾		2			

1) Note operating range of proximity sensors

2) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Forces [N]					
Piston \varnothing		16	20	25	32
Theoretical force at 6 bar, advancing ¹⁾		121	188	295	483
Theoretical force at 6 bar, returning ¹⁾		104	158	247	415

1) Theoretical values, please note: Degree of efficiency: approx. 90%


Linear modules HMP

Technical data

Weight [g]		16	20	25	32
Piston Ø					
Product weight	with 0 mm stroke	2100	4700	6300	10900
	per 10 mm stroke	88	110	150	200
Moving load	with 0 mm stroke	900	1500	2300	4000
	per 10 mm stroke	28	37	55	74
End cap	HMP-...-AD	180	270	300	400
	HMP-...-EL	210	300	330	430
Clamping unit HMP-...-KP for effective stroke	50 mm	109	114	-	-
	100 mm	120	125	-	-
	150 mm	131	136	-	-
	200 mm	142	147	-	-
	250 mm	153	158	-	-
	320 mm	168	173	-	-
Intermediate position module	HMP-...-Z1A/Z1E	165	206	227	321

Materials

Sectional view




Linear module		
1	Housing cover	Anodised aluminium
2	Yoke plate	Anodised aluminium
3	Profile	Anodised aluminium
4	Guide barrel	Tool steel
-	Seals	Nitrile rubber, polyurethane


Linear modules HMP

Technical data

Permissible torque M as a function of the stroke length l (at the yoke plate)




Permissible effective load Fq as a function of the stroke length l (at the yoke plate)




Linear modules HMP

Technical data


Deflection/deformation f as a function of the effective load m and the position l (stroke)




HMP-16




HMP-20



HMP-25



HMP-32



Linear modules HMP

Technical data



Max. permissible horizontal effective load at 6 bar


HMP-16: 10 kg

HMP-20: 20 kg


HMP-25: 30 kg

HMP-32: 50 kg


Permissible horizontal advancing time t as a function of the stroke length and the effective load m with optimum shock absorber stroke




HMP-16¹⁾




HMP-20¹⁾



HMP-25¹⁾



HMP-32¹⁾



1) Further nominal strokes in preparation

Linear modules HMP

Technical data

Max. permissible horizontal effective load at 6 bar


HMP-16: 10 kg

HMP-20: 20 kg


HMP-25: 30 kg

HMP-32: 50 kg


Permissible horizontal returning time t as a function of the stroke length and the effective load m with optimum shock absorber stroke




HMP-16¹⁾




HMP-20¹⁾



HMP-25¹⁾



HMP-32¹⁾



1) Further nominal strokes in preparation


Linear modules HMP

Technical data




Max. permissible vertical effective load at 6 bar	
without clamping cartridge	with clamping cartridge
HMP-16: 5 kg	HMP-16: 4 kg
HMP-20: 10 kg	HMP-20: 7.5 kg
HMP-25: 15 kg	
HMP-32: 25 kg	

Permissible vertical advancing time t as a function of the stroke length and the effective load m with optimum shock absorber stroke
HMP-16/-20/-25/-32¹⁾



Permissible vertical returning time t as a function of the stroke length and the effective load m with optimum shock absorber stroke
HMP-16/-20/-25/-32¹⁾



1) Further nominal strokes in preparation



Linear modules HMP

Technical data


Advancing/returning time t as a function of the optimum length L to which the shock absorber should be screwed out

In order to obtain the shortest possible travel time with a linear module HMP, it is essential to adjust the shock absorbers to match the advancing/returning time t .

The optimum length L to which the shock absorbers should be screwed out is shown in the adjacent graph.




Determining the permissible effective load



As long as the centre of gravity of the effective load on the yoke plate lies within the outline of this plate, it is impossible to overload the linear module.

Centre of gravity



When dovetail mounting components are used, the centre of gravity should be within this area.

Recommended position of centre of gravity for low-vibration operation.


Linear modules HMP

Technical data




Intermediate position module Z1A/Z1E

Intermediate position with advancing with Z1A



Range for possible intermediate positions when advancing



L1 = Rear non-operational zone
 L2 = Front non-operational zone
 L3 = Effective stroke

X = Zone for possible intermediate positions
 $X = L3 - L1 - L2$

Non-operational zones [mm]

Piston \varnothing	16	20	25	32
L1	33	42	42	55.5
L2	66	68.5	54.5	56

Calculation example

Given:
 Linear module
 HMP-16-200-...-Z1A-...

To be found:
 In which zone of the effective stroke
 are intermediate positions possible?

Calculation:
 The piston \varnothing of the linear module
 (16 mm) determines the following
 non-operational zones which do not
 permit intermediate positions:

L1 = 33 mm
 L2 = 66 mm

$X = L3 - L1 - L2 = 101 \text{ mm}$

This means:
 The lower limit of the effective stroke
 range for permissible intermediate
 positions is:
 L1 = 33 mm

The upper limit of the effective stroke
 range for permissible intermediate
 positions is:
 L1 + X = 134 mm

- - Note


Ordering data in the:

- Modular products → 24
- Accessories → 26


Linear modules HMP

Technical data

Intermediate position when returning with Z1E



Range for possible intermediate positions when returning



- L1 = Rear non-operational zone
- L2 = Front non-operational zone
- L3 = Effective stroke
- X = Zone for possible intermediate positions
- X = $L3 - L1 - L2$

Non-operational zones [mm]

Piston Ø	16	20	25	32
L1	47.5	62	54.5	56
L2	33	42	42	55.5

Calculation example

Given:
Linear module
HMP-16-200-...-Z1E-...


To be found:
In which zone of the effective stroke
are intermediate positions possible?

Calculation:
The piston Ø of the linear module
(16 mm) determines the following
non-operational zones which do not
permit intermediate positions:
L1 = 47.5 mm
L2 = 33 mm

X = $L3 - L1 - L2 = 119.5$ mm

This means:
The lower limit of the effective stroke
range for permissible intermediate
positions is:
L1 = 47.5 mm

The upper limit of the effective stroke
range for permissible intermediate
positions is:
L1 + X = 167 mm

-  Note

- Ordering data in the:
- Modular products → 24
 - Accessories → 26

Linear modules HMP


Technical data



Dimensions

Download CAD data → www.festo.com

Piston Ø 16/20 mm



Type	B1	B2	B3	B4	B5	B6	D1	D2	D3	D4	D5	D6	D7	H1	H2	H3
			±0.1				Ø H7		Ø H13				Ø H7			±0.1
HMP-16	57.8	26	8.5	51.7	34	44	9	M6	10	M5	M5		9	92	34.5	7
HMP-20	65.8	30	10	59.8		51				M5	G1/8	M5	9	107	37	7

Type	H4	H6	H7	H8	H9	H10	H11	H12	H13	H14	H17	L1	L2	L3	L4
					±0.03 ¹⁾	±0.03 ¹⁾									+0.2
HMP-16				25	60	-	40	6	33	85	38	247	23	217	15
HMP-20	4.5	13.5	40	30		20			35.5	100.4	40	320		290	

Type	L5	L6	L7	L8	L9	L10	L11	L12	L13	T1	T2	T3	T4	T6	T7	≅
		±0.03		+0.2	±0.03	±0.03	±0.03	±0.03	±0.03		+0.1			+0.1		
HMP-16	39	20	10.75	20	40	60	80	100	140	5.7	2.1	6.4	6	2.1	12	4
HMP-20	45								200			9				

1) Tolerance specification applies to countersink D1; tolerance for thread D2: ±0.2

Linear modules HMP


Technical data



Dimensions

Download CAD data → www.festo.com

Piston \varnothing 25/32 mm



- 1) 2 mounting slots for slot nuts HMBN-5-2M5
 - 2) 4 mounting slots for slot nuts HMBN-5-2M5
 - 3) Dovetail mounting facility
 - 4) Set screw for clamping of yoke plate (can be turned through 360°)
 - 5) Thread and centring hole for load attachment with centring sleeves ZBH-9
 - 6) Air connection, advancing
 - 7) Air connection, returning
- + = plus stroke length

Type	B1	B2	B3	B4	B6	B7	D1	D2	D3	D4	D5	D7	D8	D9
			±0.1				\varnothing H7		\varnothing H13			\varnothing H7	\varnothing H13	\varnothing
HMP-25	77.3	35	11	69.8	60	40	9	M6	10	M5	G $\frac{1}{8}$	9	5.5	10
HMP-32	90.8	40		79.8	70						G $\frac{1}{4}$			

Type	H1	H2	H3	H5	H6	H7	H8	H9	H10	H11	H12	H13	H14	H15	H16
			±0.1					±0.03 ¹⁾	±0.03 ¹⁾						
HMP-25	120	43	9	13	20	40	30	60	20	40	6	38	110	20	74
HMP-32	143	53					40	80				48	133	30	

Type	H17	L1	L2	L3	L4	L5	L7	L8	L13	T1	T2	T3	T4	T5	⌀
					+0.2			±0.2	±0.03		+0.1				
HMP-25	40	320	28	290	15	50	15	25	190	5.7	2.1	9	6	5.7	5
HMP-32		427		392					290			12			

1) Tolerance specification applies to countersink D1; tolerance for thread D2: ±0.2


Linear modules HMP

Technical data

FESTO

Dimensions – Pneumatic connections (code 2G3/2G4/2G6)


Download CAD data → www.festo.com



Type	B1	B2	H1	H2	H3	H4	L1	L2	⌀C1	⌀C2
HMP-16-...-2G3	17	11	33.6	19	5.5	7	20.6	15	7	9
HMP-16-...-2G4				22.6						
HMP-20-...-2G4	20	16	48.7	28.9	8		31.3	22.2	13	14
HMP-20-...-2G6				27.5		31.4				
HMP-25-...-2G4	22	20	61.8	28.9	10	9	31.3	28.2	17	17
HMP-25-...-2G6				27.5			31.4			
HMP-32-...-2G4				37.9				35.8		
HMP-32-...-2G6				38.2			35.9			

Dimensions – Clamping unit (code KP)

Download CAD data → www.festo.com



Type	D1 ∅	D2 1)	D3 ∅	L1	⌀C	Holding force [N]	Effective load	
							horizontal [kg]	vertical [kg]
HMP-16	11.4	M3	6	5	5	100	10	4
HMP-20				3.8			20	7.5

1) Air connection is supplied ready-fitted with QS connector QSM-M3-4

Note

The clamping unit must only be operated when the rod is stationary (end position). Dynamic braking operations can result in severe damage to the clamping device.

Precision positioning cannot be guaranteed with the clamping unit since slippage of approx. 1 – 2 mm can occur.

When using the linear module HMP-20 together with the clamping unit, the max. possible stroke is reduced by 12.5 mm.


Linear modules HMP

Technical data

Dimensions – Intermediate position modules

Download CAD data → www.festo.com

(code Z1A/Z1E)




- 1 Intermediate position module Z1A for advance stroke
- 2 Intermediate position module Z1E for return stroke

Dimensions – End cap

Download CAD data → www.festo.com

(code AD/EL)



Type	B1	B2	D1 ∅	H1	H2	L1	L2	
HMP-16	57.4	51.2	28.5 (PG 21)	91.3	31.5	100	44	
HMP-20	65.4	59.2		106.3	34.4			
HMP-25	76.9	69.2		37.2 (PG 29)	119	40.1	120	55
HMP-32	90.4	79.2			141.6	49.9		

Linear modules HMP

Ordering data – Modular products



M Mandatory data →

Module No.	Function	Piston Ø	Stroke	Generation	Position sensing	Pneumatic connection
537 940	HMP	16	50	B	SL	2G3
537 941		20	100			2G4
537 942		25	150			2G6
537 943		32	200			
						250
			320			
			400			
Ordering example						
537 940	HMP	- 16	- 150	- B	- SL	- 2G3

Ordering table

Size	16	20	25	32	Condi- tions	Code	Enter code
M Module No.	537 940	537 941	537 942	537 943			
Function	Linear module with ball bearing guide					HMP	HMP
Piston Ø [mm]	16	20	25	32		-...	
Stroke [mm]	50	50	-	-		-50	
	100	100	100	100		-100	
	150	150	150	150		-150	
	200	200	200	200		-200	
	250	250	250	250		-250	
	320	320	320	320		-320	
	-	400	400	400		-400	
Generation	B series					-B	-B
Position sensing	Sensor strip					-SL	-SL
Pneumatic connection	One-way flow control valve, 3 mm barbed connector	-	-	-		-2G3	
	One-way flow control valve, 4 mm barbed connector					-2G4	
	-	One-way flow control valve, 6 mm barbed connector				-2G6	

Transfer order code

Linear modules HMP

Ordering data – Modular products



Options								
Clamping unit	Intermediate position	Interface	Proximity sensor set	User documentation	Accessories	Cable with socket	Slot cover	Centring sleeves
KP	Z1A Z1E	AD EL	A1 A2 A3 A4 A5 A6	E S F I V B	ZUB	...V	A	...Z
-	- Z1A	- EL	- A1	- B	ZUB	- 2V		

Ordering table								
Size	16	20	25	32	Condi- tions	Code		Enter code
0 Clamping unit	Attached					1	-KP	
Intermediate position	1 intermediate position, advancing					2	-Z1A	
	1 intermediate position, returning					2	-Z1E	
Interface	End cap						-AD	
	End cap with electrical interface						-EL	
Proximity sensor, assembled	Proximity sensor with cable, 2.5 m						-A1	
	Proximity sensor, contactless, NPN with cable, 2.5 m						-A2	
	Proximity sensor, contactless, PNP with cable, 2.5 m						-A3	
	Proximity sensor with plug M8					3	-A4	
	Proximity sensor, contactless, NPN with plug M8					3	-A5	
	Proximity sensor, contactless, PNP with plug M8					3	-A6	
Alternative user documentation (standard is German/English)	User documentation, English						-E	
	User documentation, Spanish						-S	
	User documentation, French						-F	
	User documentation, Italian						-I	
	User documentation, Swedish						-V	
	Express waiver - no manual to be included (already available)						-B	
Accessories	Supplied separately						ZUB-	ZUB-
Cable with socket, 2.5 m	1 ... 10						...V	
Slot cover	Slot cover						A	
Centring sleeves (pack of 10)	10, 20, 30, 40, 50, 60, 70, 80, 90						...Z	

1 KP Not with intermediate position Z1A, Z1E.

2 Z1A, Z1E Min. stroke: 150 mm.

3 A4, A5, A6 Not with interface EL

Max. stroke: Piston Ø 16, 20, 25 mm: 200 mm
Piston Ø 32 mm: 150 mm





Transfer order code

- - - - - **ZUB** -

Linear modules HMP

Accessories

FESTO



Ordering data						
	For piston \varnothing [mm]	Remarks	Order code	Part No.	Type	PU ¹⁾
Intermediate position module BZ1-HMP						
	16	For advance movement	Z1A	538904	BZ1-HMP-16-B-Z1A	1
	20			538905	BZ1-HMP-20-B-Z1A	
	25			538906	BZ1-HMP-25-B-Z1A	
	32			538907	BZ1-HMP-32-B-Z1A	
	16	For return movement	Z1E	538908	BZ1-HMP-16-B-Z1E	
	20			539909	BZ1-HMP-20-B-Z1E	
	25			538910	BZ1-HMP-25-B-Z1E	
	32			538911	BZ1-HMP-32-B-Z1E	
Centring sleeve ZBH Technical data → Internet: zbh						
	16 ... 32	For yoke plate	Z	150927	ZBH-9	10
Slot cover ABP						
	16 ... 32	For sensor strip every 0.5 m	A	151681	ABP-5	2
Shock absorber YSRW Technical data → Internet: ysrw						
	16	-	-	191194	YSRW-8-14	1
	20			191196	YSRW-12-20	
	25			191196	YSRW-12-20	
	32			191197	YSRW-16-26	




1) Packaging unit quantity

Linear modules HMP

Accessories

FESTO


Ordering data – Proximity sensors for T-slot, magneto-resistive						Technical data → Internet: smt	
	Type of mounting	Switch output	Electrical connection	Cable length [m]	Part No.	Type	
N/O contact							
	Insertable in the slot from above, flush with cylinder profile, short design	PNP	Cable, 3-wire	2.5	574335	SMT-8M-A-PS-24V-E-2,5-OE	
			Plug M8x1, 3-pin	0.3	574334	SMT-8M-A-PS-24V-E-0,3-M8D	
			Plug M12x1, 3-pin	0.3	574337	SMT-8M-A-PS-24V-E-0,3-M12	
		NPN	Cable, 3-wire	2.5	574338	SMT-8M-A-NS-24V-E-2,5-OE	
			Plug M8x1, 3-pin	0.3	574339	SMT-8M-A-NS-24V-E-0,3-M8D	
N/C contact							
	Insertable in the slot from above, flush with cylinder profile, short design	PNP	Cable, 3-wire	7.5	574340	SMT-8M-A-PO-24V-E-7,5-OE	



Ordering data – Proximity sensors for T-slot, magnetic reed						Technical data → Internet: sme		
	Type of mounting	Switch output	Electrical connection	Cable length [m]	Part No.	Type		
N/O contact								
	Insertable in the slot from above, flush with cylinder profile	Contacting	Cable, 3-wire	2.5	543862	SME-8M-DS-24V-K-2,5-OE		
				5.0	543863	SME-8M-DS-24V-K-5,0-OE		
			Plug M8x1, 3-pin	Cable, 2-wire	2.5	543872	SME-8M-ZS-24V-K-2,5-OE	
				0.3	543861	SME-8M-DS-24V-K-0,3-M8D		
	Insertable in the slot lengthwise, flush with the cylinder profile	Contacting	Cable, 3-wire	2.5	150855	SME-8-K-LED-24		
			Plug M8x1, 3-pin	0.3	150857	SME-8-S-LED-24		
N/C contact								
	Insertable in the slot lengthwise, flush with the cylinder profile	Contacting	Cable, 3-wire	7.5	160251	SME-8-O-K-LED-24		



Linear modules HMP

Accessories

FESTO

Ordering data – Proximity sensors for C-slot, magneto-resistive						Technical data → Internet: smt
	Type of mounting	Switch output	Electrical connection, connection direction	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above	PNP	Cable, 3-wire, in-line	2.5	551373	SMT-10M-PS-24V-E-2,5-L-OE
			Plug M8x1, 3-pin, in-line	0.3	551375	SMT-10M-PS-24V-E-0,3-L-M8D
			Plug M8x1, 3-pin, lateral	0.3	551376	SMT-10M-PS-24V-E-0,3-Q-M8D

Ordering data – Proximity sensors for C-slot, magnetic reed						Technical data → Internet: sme
	Type of mounting	Switch output	Electrical connection, connection direction	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above	Contacting	Plug M8x1, 3-pin, in-line	0.3	551367	SME-10M-DS-24V-E-0,3-L-M8D
			Cable, 3-wire, in-line	2.5	551365	SME-10M-DS-24V-E-2,5-L-OE
			Cable, 2-wire, in-line	2.5	551369	SME-10M-ZS-24V-E-2,5-L-OE
	Insertable in the slot lengthwise	Contacting	Plug M8x1, 3-pin, in-line	0.3	173212	SME-10-SL-LED-24
			Cable, 3-wire, in-line	2.5	173210	SME-10-KL-LED-24

Ordering data – Connecting cables					Technical data → Internet: nebu
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541333	NEBU-M8G3-K-2.5-LE3
			5	541334	NEBU-M8G3-K-5-LE3
	Straight socket, M12x1, 5-pin	Cable, open end, 3-wire	2.5	541363	NEBU-M12G5-K-2.5-LE3
			5	541364	NEBU-M12G5-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541338	NEBU-M8W3-K-2.5-LE3
			5	541341	NEBU-M8W3-K-5-LE3
	Angled socket, M12x1, 5-pin	Cable, open end, 3-wire	2.5	541367	NEBU-M12W5-K-2.5-LE3
			5	541370	NEBU-M12W5-K-5-LE3


Linear modules HMP




Accessories

FESTO

Adapter kit
DHAA, HMAV, HMSV

Material:
Wrought aluminium alloy
Free of copper and PTFE
RoHS-compliant

 Note
The kit includes the individual mounting interface as well as the necessary mounting material.

Permissible drive/drive combinations with adapter kit			Download CAD data → www.festo.com				
Combination	1	2	Adapter kit				
	Drive	Drive	CRC ¹⁾	Part No.	Type	Required quantity	PU ²⁾
	HMP	HMP	HMSV				
	Direct mounting						
	16	16	2	–	M5x25 DIN 912 ³⁾	2	–
				150927	ZBH-9 ³⁾	2	10
	20	16, 20		–	M5x25 DIN 912 ³⁾	3	–
				150927	ZBH-9 ³⁾	3	10
	25, 32	16, 20		–	M5x30 DIN 912 ³⁾	3	–
				150927	ZBH-9 ³⁾	3	10
	25	25		177652	HMSV-6	–	–
	32	25, 32		177652	HMSV-6	–	–
	Dovetail mounting						
	16, 20, 25	16	2	177647	HMSV-1	1	1
	20	20		177649	HMSV-3	1	1
	25	20, 25		177649	HMSV-3	1	1
32	16	177649		HMSV-3	1	1	
32	20, 25, 32	177653		HMSV-7	1	1	
DGC/HMP	DGC	HMP	DHAA, HMAV				
	25	16, 20	2	176005	HMAV-DL25	1	1
	32	16, 20		562150	DHAA-D-L-32-H2	1	1
	40	20, 25, 32		562151	DHAA-D-L-40-H2	1	1
DGP(I)L, DGE/HMP	DG...	HMP	HMAV				
	25	16, 20	2	176005	HMAV-DL25	1	1
	32	16, 20, 25		176006	HMAV-DL32	1	1
	40	20, 25, 32		176007	HMAV-DL40	1	1

- Corrosion resistance class CRC 2 to Festo standard FN 940070
Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.
- Packaging unit quantity
- The screws and centring sleeves listed are not included in the scope of delivery of the drives


Linear modules HMP


Accessories



Adapter kit
DHAA, HMAV, HMSV

Material:
Wrought aluminium alloy
Free of copper and PTFE
RoHS-compliant

 Note
The kit includes the individual mounting interface as well as the necessary mounting material.


Permissible drive/drive combinations with adapter kit			Download CAD data → www.festo.com				
Combination	[1] Drive	[2] Drive	Adapter kit			Required quantity	PU ²⁾
	Size	Size	CRC ¹⁾	Part No.	Type		
EGC/HMP	EGC	HMP	DHAA, HMAV				
	80	16, 20	2	176005	HMAV-DL25	1	1
	120	20, 25, 32		562151	DHAA-D-L-40-H2	1	1

- 1) Corrosion resistance class CRC 2 to Festo standard FN 940070
Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.
- 2) Packaging unit quantity

Product Range and Company Overview

A Complete Suite and Company Overview

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drivers



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 16,000 employees in 60 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.




© Copyright 2013, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmental friendly printing plant.

Festo North America



**1 Festo Canada
Headquarters
Festo Inc.**
5300 Explorer Drive
Mississauga, ON
L4W 5G4

2 Montréal
5600, Trans-Canada
Pointe-Claire, QC
H9R 1B6

3 Québec City
2930, rue Watt#117
Québec, QC
G1X 4G3



**4 Festo United States
Headquarters
Festo Corporation**
395 Moreland Road
Hauppauge, NY
11788

5 Appleton
North 922 Tower View Drive, Suite N
Greenville, WI
54942

7 Detroit
1441 West Long Lake Road
Troy, MI
48098

6 Chicago
85 W Algonquin - Suite 340
Arlington Heights, IL
60005

8 Silicon Valley
4935 Southfront Road, Suite F
Livermore, CA
94550

Festo Regional Contact Center

Canadian Customers

Commercial Support:
Tel: 1 877 GO FESTO (1 877 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: festo.canada@ca.festo.com

Technical Support:
Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: technical.support@ca.festo.com

USA Customers

Commercial Support:
Tel: 1 800 99 FESTO (1 800 993 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: customer.service@us.festo.com

Technical Support:
Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: product.support@us.festo.com