


Proportional pressure regulators VPPM, NPT



Proportional pressure regulators VPPM, NPT

Key features

FESTO



Innovative

- Multi-sensor control (cascade control)
- Diagnostics
- Choice of regulation characteristic
- Temperature compensated
- High dynamic response
- High repetition accuracy
- Modular product system

Versatile

- Individual valves (in-line valve)
- Various user interfaces
 - LED displays
 - LCD display
 - Adjustment/selection buttons
- Choice of valves with different pressure ranges
- Pressure range can be modified on the valve
- Choice of different setpoint specifications
 - Current input
 - Voltage input

Reliable

- Integrated pressure sensor with separate output
- Cable break monitoring
- Pressure is maintained if the controller fails

Easy to mount


- H-rail mounting
- Individually via mounting bracket
- QS fittings

Proportional pressure regulators VPPM, NPT

Key features

FESTO

VPPM on the valve terminal type 32 MPA



Innovative

- Multi-sensor control
- Diagnostics via the bus
- Choice of regulation characteristic
- High dynamic response
- 2 accuracy levels

Versatile

- For all common protocols
- As an individual pressure regulator
- As a pressure zone regulator
- Choice of 3 valves with different pressure ranges
- 3 pressure ranges (presets) can be set via the bus
- Internal or external compressed air supply possible

Reliable

- Long service life
- LED display for the operating status
- Pressure is maintained if the supply voltage fails
- Fast troubleshooting thanks to LEDs on the valves and diagnostics via fieldbus
- Ease of servicing through replaceable valves

Easy to mount

- Easy replacement of the valves
- Tested units
- Easy extension of the valve terminal


-  - Note

More information on the VPPM valves for type 32 MPA
 → type 32

Proportional pressure regulators VPPM, NPT

Key features

Layout of a control circuit



Setup

The figure shows a closed-loop control circuit. The reference variable w (setpoint value, e.g. 5 volts or 8 mA) initially acts on a comparator. The measuring device sends the value of the controlled variable x (actual value, e.g. 3 bar) to the comparator as a feedback signal r . The closed-loop control element detects the system deviation e and actuates the final con-


trol element. The output of the final control element acts on the controlled system. The closed-loop control element thus attempts to compensate for the difference between the reference variable w and the controlled variable x by using the final control element.

Method of operation

This process runs continuously so changes in the reference variable are always detected. However, a system deviation will also appear if the reference variable is constant but the controlled variable changes. This happens when the flow through the valve changes in response to a switching action, a cylinder movement or

a change in load. The disturbance variable z will also cause a system deviation. An example of this is when the pressure drops in the air supply. The disturbance variable z acts on the controlled variable x unintentionally. In all cases, the regulator attempts to readjust the controlled variable x to the reference variable w .

Multi-sensor control (cascade control) of the VPPM



Cascade control

Unlike conventional direct-acting regulators, with multi-sensor control several control circuits are nested inside each other. The overall controlled

system is divided into smaller sub-controlled circuits that are easier to control for the specific task.

Control precision


Multi-sensor control significantly improves control precision and dynamic response in comparison with single-acting regulators.

Proportional pressure regulators VPPM, NPT

Key features


Terms related to the proportional pressure regulator

Hysteresis




There is always a linear relationship within a certain tolerance between the setpoint value entered and the pressure output. Nevertheless it makes a difference whether the setpoint value is entered as rising or falling. The difference between the maximum deviations is referred to as hysteresis.

Linearity error




A perfectly linear progression of the control characteristic of the output pressure is theoretical. The maximum percentage deviation from this theoretical control characteristic is referred to as the linearity error. The percentage value refers to the maximum output pressure (full scale).

Response sensitivity




The response sensitivity of the device determines how sensitively one can change, i.e. adjust, a pressure. The smallest setpoint value difference that results in a change in the output pressure is referred to as the response sensitivity. In this case, 0.01 bar.

Repetition accuracy (reproducibility)




The repetition accuracy is the margin within which the fluid output variables are scattered when the same electrical input signal coming from the same direction is repeatedly adjusted. The repetition accuracy is expressed as a percentage of the maximum fluid output signal.

Zero offset




If, for example, a VPPM cannot be vented for safety reasons, the minimum pressure can be increased from the zero point. The smallest setpoint value is then assigned an output pressure of 5 bar, for example, and the largest setpoint value an output pressure of 10 bar. Zero suppression is automatically switched off if zero offsetting is used.

Pressure range adaptation



In the delivery condition, 100% setpoint value equals 100% fluid output signal. Pressure range adaptation or adjustment enables the fluid output variable to be matched to the setpoint value.




Zero point suppression



In practice it is possible that there is residual voltage or residual current at the setpoint input of the VPPM via the setpoint generator. Zero point suppression is used so that the valve is reliably vented at a setpoint value of zero.

Proportional pressure regulators VPPM, NPT


Product range overview

Function	Version	Design	Pneumatic connection 1, 2, 3	Nominal size pressurise/ exhaust [mm]	Pressure regulation range [psi]	Setpoint value input			→ Page/ Internet
						Voltage type 0 ... 10 V	Current type 4 ... 20 mA	Digital –	
Pressure regulators	LED operator unit (standard)								
		Pilot actuated diaphragm valve	1/8 NPT	6/4.5	0 ... 29.4/0 ... 2 0 ... 88.2/0 ... 6 0 ... 147/0 ... 10	■	■	–	12
			1/4 NPT	8/7	0 ... 29.4/0 ... 2 0 ... 88.2/0 ... 6 0 ... 147/0 ... 10	■	■	–	
	LCD operator unit								
		Pilot actuated diaphragm valve	1/8 NPT	6/4.5	0 ... 29.4/0 ... 2 0 ... 88.2/0 ... 6 0 ... 147/0 ... 10	■	■	–	12
			1/4 NPT	8/7	0 ... 29.4/0 ... 2 0 ... 88.2/0 ... 6 0 ... 147/0 ... 10	■	■	–	
			1/2 NPT	12/12	0 ... 88.2/0 ... 6 0 ... 147/0 ... 10	■	■	–	
	LED operator unit, for valve terminal MPA-S								
		Pilot actuated diaphragm valve	Sub-base MPA	6/4.5, 8/7	0 ... 29.4/0 ... 2 0 ... 88.2/0 ... 6 0 ... 147/0 ... 10	–	–	■	mpas

Proportional pressure regulators VPPM, NPT

Peripherals overview

Individual valve VPPM-6L ...




Accessories		Description	→ Page/Internet
1	Angled plug socket with cable NEBU-M12W8-...	–	28
2	Straight plug socket with cable SIM-M12-8GD-...	–	28
3	Proportional pressure regulator VPPM	Operator unit with LED	12
4	Proportional pressure regulator VPPM	Operator unit with LCD	12
5	Push-in fitting QS	For connecting compressed air tubing with standard O.D.	qs
6	Silencer	For fitting in exhaust ports	u
7	Bracket VAME-P1-A	For mounting the valve	25
8	H-rail mounting VAME-P1-T	For mounting on a H-rail	26

Proportional pressure regulators VPPM, NPT

Peripherals overview

Individual valve VPPM-12L ...




Accessories		
	Description	→ Page/Internet
1	Plug socket with cable, angled NEBU-M12W8-...	38
2	Plug socket with cable, straight SIM-M12-8GD-...	38
3	Fixing screws	-
4	Reguladores de presión proporcionales VPPM	Operator unit with LED or LCD 14
5	Push-in fitting QS	For connecting compressed air tubing with standard outside diameter qs
6	Silencer	For fitting on exhaust ports u

Proportional pressure regulators VPPM, NPT

System overview

VPPM-6TA ... , VPPM-8TA ... for valve terminal MPA-S



Accessories		
	Description	→ Page/Internet
1	Valve terminal type 32 MPA With fieldbus connection and VPPM	mpas
2	Proportional pressure regulator VPPM For valve terminal type 32 MPA-S	mpas
3	Electrical interlinking module VMPA1-FB-EV-AB For sub-base of the proportional pressure regulator	mpas
4	Sub-base VMPA-FB-AP-P1 Without electrical interlinking module and without electrical module	mpas
5	Push-in fitting QS	qs
6	Mounting attachment VMPA-BG	mpas

Proportional pressure regulators VPPM, NPT

Type codes

VPPM – 6 L – L – 1 – N18 – 0L 6H – 1L – 6H

Type

VPPM	Modular proportional pressure regulator
------	---

Nominal size

6	6 mm
8	8 mm
12	12 mm

Design

L	In-line valve
F	Flanged valve
T	Flanged valve for valve terminal

Mounting method

–	Freely mountable
A	Valve terminal MPA
G	H-rail
P	Manifold PR

Dynamic response class

L	Low
---	-----

Valve function

1	3/2-way solenoid valve, normally closed
---	---

Pneumatic connection

N18	Thread 1/8NPT
N14	Thread 1/4NPT
N12	Thread 1/2NPT

Lower pressure value of regulation range

0L	0 bar
----	-------

Upper pressure value of regulation range

2H	2 bar
6H	6 bar
10H	10 bar

Alternative lower pressure value of regulation range


... L	0 - 9 bar
-------	-----------

Alternative upper pressure value of regulation range

... H	0.2 - 10 bar
-------	--------------

Proportional pressure regulators VPPM, NPT




Type codes




Setpoint specification for individual valve	
-	For valve terminals / servo pneumatics
V1	0 ... 10 V
A4	4 ... 20 mA
Switching output	
N	Negative switching
P	Positive switching
Accuracy	
-	2% (standard)
S1	1%
Operator unit	
-	LED (standard)
C1	With LCD, pressure unit variable

Proportional pressure regulators VPPM, NPT

Technical data


-  - Flow rate
380 ... 7,000 l/min
-  - Voltage
21.6 ... 26.4 V DC
-  - Pressure regulation range
0 ... 147 psi
0 ... 10 bar

- Variants
- Setpoint input as analogue voltage signal 0 ... 10 V
 - Setpoint input as analogue current signal 4 ... 20 mA
 - LED version
 - With LCD display (... C1)
 - NPN (N) or PNP (P) switching output



General technical data			1/8 NPT	1/4 NPT	1/2 NPT
Valve function			3-way proportional pressure regulator		
Design			Piloted diaphragm regulator		
Sealing principle			Soft		
Actuation type			Electric		
Type of control			Piloted		
Type of reset			Mechanical spring		
Type of mounting			Via through-hole, via accessories		
Mounting position			Any		
Nominal size	Pressurisation	[mm]	6	8	12
	Exhaust	[mm]	4.5	7	12
Standard nominal flow rate		[l/min]	→ Graphs		
Product weight		[g]	400	500	2,050

Electrical data			VPPM-6	VPPM-8	VPPM-12
Electrical connection			Plug, round design, 8-pin, M12		
Operating voltage range		[V DC]	24 ± 10% = 21.6 ... 26.4		
Residual ripple		[%]	10		
Duty cycle		[%]	100		
Max. electrical power consumption		[W]	7		12
Setpoint input signal	Voltage	[V DC]	0 ... 10		
	Current	[mA]	4 ... 20		
Protection against short circuit			For all electrical connections		
Reverse polarity protection			For all electrical connections		
Protection class			IP65		


-  - Note
Output pressure is maintained unregulated if the power supply cable is interrupted.

Proportional pressure regulators VPPM, NPT


Technical data

Flow rate q_n from 1 \rightarrow 2 as a function of output pressure p_2


VPPM-6L-...-0L2H-... (29.4 psi/2 bar)



VPPM-6L-...-0L6H-... (88.2 psi/6 bar)




VPPM-6L-...-0L10H-... (147 psi/10 bar)




Flow rate q_n from 2 \rightarrow 3 as a function of output pressure p_2


VPPM-6L-...-0L2H-... (29.4 psi/2 bar)



VPPM-6L-...-0L6H-... (88.2 psi/6 bar)



VPPM-6L-...-0L10H-... (147 psi/10 bar)



Proportional pressure regulators VPPM, NPT


Technical data

FESTO

Flow rate q_n from 1 \rightarrow 2 as a function of output pressure p_2


VPPM-8L-...-0L2H-...

(29.4 psi/2 bar)




VPPM-8L-...-0L6H-...

(88.2 psi/6 bar)



VPPM-8L-...-0L10H-...


(147 psi/10 bar)



Flow rate q_n from 2 \rightarrow 3 as a function of output pressure p_2


VPPM-8L-...-0L2H-...

(29.4 psi/2 bar)



VPPM-8L-...-0L6H-...

(88.2 psi/6 bar)



VPPM-8L-...-0L10H-...

(147 psi/10 bar)




Proportional pressure regulators VPPM, NPT


Technical data

Flow rate q_n from 1 → 2 as a function of output pressure p_2


VPPM-8F/8TA-...-0L2H-... (29.4 psi / 2 bar)



VPPM-8F/8TA-...-0L6H-... (88.2 psi / 6 bar)




VPPM-8F/8TA-...-0L10H-... (147 psi / 10 bar)



Flow rate q_n from 2 → 3 as a function of output pressure p_2


VPPM-8F/8TA-...-0L2H-... (29.4 psi / 2 bar)



VPPM-8F/8TA-...-0L6H-... (88.2 psi / 6 bar)



VPPM-8F/8TA-...-0L10H-... (147 psi / 10 bar)




Proportional pressure regulators VPPM, NPT

Technical data




Flow rate q_n from 1 → 2 as a function of output pressure p_2


VPPM-12L-...-0L2H-... (4 bar)



VPPM-12L-...-0L6H-... (8 bar)




VPPM-12L-...-0L10H-... (11 bar)




Flow rate q_n from 2 → 3 as a function of output pressure p_2

VPPM-12L-...-0L2H-... (4 bar)



VPPM-12L-...-0L6H-... (8 bar)



VPPM-12L-...-0L10H-... (11 bar)



Proportional pressure regulators VPPM, NPT


Technical data

Operating and environmental conditions				
Pressure regulation range	[psi]	0 ... 29.4	0 ... 88.2	0 ... 147
	[bar]	0.02 ... 2	0.06 ... 6	0.1 ... 10
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4] Inert gases			
Note on operating/pilot medium	Operation with lubricated medium not possible			
Supply pressure 1 ¹⁾	[bar]	2 ... 4	2 ... 8	2 ... 11
Max. pressure hysteresis	[mbar]	10	30	50
FS (full scale) linearity error	[%]	± 0.5		
FS (full scale) repetition accuracy	[%]	0.5		
Temperature coefficient	[%/K]	0.04		
Ambient temperature, operator unit LED (standard)	[°C]	0 ... 60		
Ambient temperature, operator unit with LCD	[°C]	0 ... 50		
Temperature of medium	[°C]	10 ... 50		
Note on materials	RoHS-compliant			
Corrosion resistance class	[CRC]	2 ²⁾		
CE mark	To EU EMC Directive (see declaration of conformity) ³⁾			
Certification	RCM trademark			
	c UL us - Listed (OL)			


- 1) Supply pressure 1 should always be 1 bar greater than the maximum regulated output pressure.
- 2) Corrosion resistance class 2 as per Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 3) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com/sp → User documentation.
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

Materials

Sectional view VPPM-6 ..., VPPM-8 ...



Sectional view VPPM-12 ...



1	Housing	Wrought aluminium alloy
2	Diaphragm	Nitrile rubber

Proportional pressure regulators VPPM, NPT

Technical data




Dimensions

Download CAD data → www.festo.com

VPPM-6L

With LCD




1 Socket head screw M4x65

Type	B1	B2	B3	D1 Ø	D2 Ø	D4 Ø	H1	H2	H3	H4	H6	H7	H9	H10	H12
VPPM-6L	65.5	47.5	16	1/8 NPT	M12	4.4	126.9	110.4	80.1	52.8	42	27	26.3	23	12

Type	L1	L2	L6
VPPM-6L	41.5	31.5	25

M12 – Pin allocation



- | | | |
|---------------------------|---------------------|---------------------|
| 1 Digital input D1 | 4 Analogue input W+ | 7 0 V DC or GND |
| 2 +24 V DC supply voltage | 5 Digital input D2 | 8 Digital output D3 |
| 3 Analogue input W- | 6 Analogue output X | |

Proportional pressure regulators VPPM, NPT

Technical data




Dimensions

Download CAD data → www.festo.com

VPPM-8L

With LCD



Type	B1	B2	B3	D1 Ø	D2 Ø	H1	H2	H3	H4	H6	H7	H9	H10	H12
VPPM-8L	77.4	59.5	22	¼ NPT	M12	126.9	110.4	80	52.8	42	27	26.3	23	12

Type	L1	L2	L6
VPPM-8L	47	31.5	25

Proportional pressure regulators VPPM, NPT


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

VPPM-6TA




1 Socket head screw M4x55

Type	B1	D5 Ø	H2	H3	H4	H5	H8	H9	H11
VPPM-6TA	55.1	6	110.4	95.5	52.8	41.3	28.3	26.3	12.2

Type	L1	L2	L3	L4	L5	L6
VPPM-6TA	41.5	31.5	30.3	28.4	12.3	9.9

VPPM-8TA with LCD



1 Socket head screw M4x77

Type	B1	B2	B3	D1	D2	D5 Ø	H1	H2	H3	H4	H5	H6	H7	H8	H9	H10	H11	H12	H13
VPPM-8TA	77.4	-	-	-	-	8	-	110.4	80	52.8	41.3	-	-	28.3	26.3	23	12.2	-	95.5

Type	L1	L2	L3	L4	L5	L6	L7
VPPM-8TA	41.5	31.5	29.3	28.4	12.3	25	9.9

Proportional pressure regulators VPPM


Technical data



Dimensions

Download CAD data → www.festo.com
with LCD

VPPM-12L



Type	B1	B2	B3	B4	D1 Ø	D2	D4 Ø	H1	H2	H3	H4	H6	H7	H9	H10	H12	H13
VPPM-12L	107.4	89.5	36	74	1/2 NPT	M12	5.5	162.8	146.3	116	78.2	63	38.5	33.2	23	16.5	35.9

Type	L1	L2	L6	L7
VPPM-12L	72	53	25	9.5

Proportional pressure regulators VPPM, NPT

FESTO

Technical data

Ordering data				
Proportional pressure regulators VPPM	Pneumatic connection 1, 2, 3	Pressure regulation range [bar]	Part No.	Type
Voltage type 0 ... 10 V				
Overall accuracy 2%	1/8 NPT	0.06 ... 6	542212	VPPM-6L-L-1-N18-0L6H-V1N
			558349	VPPM-6L-L-1-N18-0L6H-V1N-C1
			558343	VPPM-6L-L-1-N18-0L6H-V1P-C1
Overall accuracy 1%	1/8 NPT	0.1 ... 10	558348	VPPM-6L-L-1-N18-0L10H-V1N-S1C1
			558341	VPPM-6L-L-1-N18-0L10H-V1P-S1C1
			558348	VPPM-6L-L-1-N18-0L10H-V1N-S1C1
	1/2 NPT	0.06 ... 6	576680	VPPM-12L-L-1-N12-0L6H-V1P-S1C1
			0.1 ... 10	576681
Current type 4 ... 20 mA				
Overall accuracy 2%	1/8 NPT	0.06 ... 6	558344	VPPM-6L-L-1-N18-0L6H-A4P-C1
		0.1 ... 10	542216	VPPM-6L-L-1-N18-0L10H-A4N
Overall accuracy 1%	1/8 NPT	0.02 ... 2	542208	VPPM-6L-L-1-N18-0L2H-A4N-S1
		0.1 ... 10	558342	VPPM-6L-L-1-N18-0L10H-A4P-S1C1
	1/2 NPT	0.06 ... 6	576682	VPPM-12L-L-1-N12-0L6H-A4P-S1C1
		0.1 ... 10	576683	VPPM-12L-L-1-N12-0L10H-A4P-S1C1
For valve terminal				
Overall accuracy 2%	Via valve terminal	0.02 ... 2	542220	VPPM-6TA-L-1-F-0L2H-N
			572410	VPPM-8TA-L-1-F-0L2H-C1
		0.06 ... 6	542221	VPPM-6TA-L-1-F-0L6H-N
			572411	VPPM-8TA-L-1-F-0L6H-C1
		0.02 ... 10	542222	VPPM-6TA-L-1-F-0L10H-N
			572412	VPPM-8TA-L-1-F-0L10H-C1
Overall accuracy 1%	Via valve terminal	0.02 ... 2	542217	VPPM-6TA-L-1-F-0L2H-N-S1
			572407	VPPM-8TA-L-1-F-0L2H-S1C1
		0.06 ... 6	542218	VPPM-6TA-L-1-F-0L6H-N-S1
			572408	VPPM-8TA-L-1-F-0L6H-S1C1
		0.02 ... 10	542219	VPPM-6TA-L-1-F-0L10H-N-S1
			572409	VPPM-8TA-L-1-F-0L10H-S1C1

Proportional pressure regulators VPPM, NPT

Ordering data – Modular products

M Mandatory data →

Module No.	Design	Nominal size	Valve type	Dynamic response	Valve operating mode	Connection type
546953	VPPM (NPT)	6	L	L	1	N18
546954		8	L			N14
546956		12	L			N12
Ordering example						
546953	VPPM	- 6	L	- L	- 1	- N18

Ordering table		Condi-tions	Code	Enter code
Size	6			
M Module No.	546953			
Design	Modular pressure regulator		VPPM	VPPM
Nominal size	6		-6	
	8		-8	
	12		-12	
Valve type	In-line	1	L	
Dynamic response	Low dynamic response (pilot-actuated, soft-sealing)		-L	-L
Valve operating mode	3/2-way valve, normally closed		-1	-1
Connection type	NPT thread 1/8 NPT		-N18	
	NPT thread 1/4 NPT		-N14	
	NPT thread 1/2 NPT		-N12	

1 L Only with connection type N18, N14, N12 (NPT thread 1/8 NPT, 1/4 NPT, 1/2 NPT)

Order code

546953
VPPM
-
6
-
L
-
1
-

Proportional pressure regulators VPPM, NPT

Ordering data – Modular products

Mandatory data					Options	
Pressure regulation range	Alternative lower pressure regulation range	Alternative upper pressure regulation range	Setpoint specification	Switching output	Overall accuracy	Operator unit
0L2H 0L6H 0L10H	–	–	V1 A4	P N	S1	C1
–	6.5L	7.1H	– A4	P	– S1	C1

Ordering table						
Size		6	Condi- tions	Code	Enter code	
M	Pressure regulation range	0 ... 29.4 psi		-0L2H		
		0 ... 88.2 psi		-0L6H		
		0 ... 147 psi		-0L10H		
	Alternative lower pressure regulation range	–	[2]	-...L		
	Alternative upper pressure regulation range	–	[3]	...H		
	Setpoint specification	Voltage (standard 0 ... 10 V)			-V1	
		Current (standard 4 ... 20 mA)			-A4	
Switching output	PNP switching			P		
	NPN switching			N		
O	Overall accuracy	1%		-S1		
	Operator unit	With LCD, pressure unit variable		C1		

[2] ...L Not with pressure regulation range (0L2H, 0L6H, 0L10H).
Must always be less than alternative upper pressure regulation range H

[3] ...H Not with pressure regulation range (0L2H, 0L6H, 0L10H).
Must always be greater than alternative lower pressure regulation range L

Transfer order code

– – –


Proportional pressure regulators VPPM, NPT

Accessories

FESTO


Bracket
VAME-P1-A

Material:
Wrought aluminium alloy, steel



Dimensions

Download CAD data → www.festo.com



1) Socket head screw M4

2) Proportional pressure regulator VPPM

3) Bracket can be reversed if required

Ordering data

Weight [g]	CRC	Part No.	Type
71	1 ¹⁾	542251	VAME-P1-A

1) Corrosion resistance class 1 according to Festo standard 940 070

Components subject to low corrosion stress. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

-  - Note

In-line valves VPPM-6L-... must be used in combination with the bracket VAME-P1-A.


Proportional pressure regulators VPPM, NPT

Accessories

FESTO


H-rail mounting
VAME-P1-T

Material:
Wrought aluminium alloy, steel



Dimensions

Download CAD data → www.festo.com



Ordering data

Weight [g]	CRC	Part No.	Type
150	1 ¹⁾	542255	VAME-P1-T

1) Corrosion resistance class 1 according to Festo standard 940 070
Components subject to low corrosion stress. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

- Note

In-line valves VPPM-6L... must be used in combination with the H-rail VAME-P1-T.


Proportional pressure regulators VPPM, NPT

Accessories

FESTO


Connecting cable NEBV-M12G8-KD-3-M12G4

For connecting the proportional pressure regulator VPPM to the analogue input and output modules of the CPX terminal.



Dimensions and pin allocation

Download CAD data → www.festo.com




Proportional pressure regulators VPPM, NPT

Accessories




Connecting cable
NEBV-M12G8-K-5-M12G4

For connecting the proportional pressure regulator VPPM to the analogue output modules of the CPX terminal.



Dimensions and pin allocation

Download CAD data → www.festo.com



Type	2	1	L
NEBV-M12G8-K-2-M12G4	Straight socket, M12, 8-pin, to VPPM	Straight plug, M12, 4-pin, to CPX module	2 m
NEBV-M12G8-K-5-M12G4			5 m

Ordering data

Description		Part No.	Type
Connecting cable		Technical data → Internet: plug socket with cable	
	Straight socket, 8-pin, M12	2 m	525616 SIM-M12-8GD-2-PU
		5 m	525618 SIM-M12-8GD-5-PU
		10 m	570008 SIM-M12-8GD-10-PU
	Angled socket, 8-pin, M12	2 m	542256 NEBU-M12W8-K-2-N-LE8
		5 m	542257 NEBU-M12W8-K-5-N-LE8
		10 m	570007 NEBU-M12W8-K-10-N-LE8
	One straight socket, 8-pin, and one straight plug, 4-pin	2 m	553575 NEBV-M12G8-K-2-M12G4
		5 m	553576 NEBV-M12G8-K-5-M12G4
	One straight socket, 8-pin, and two straight plugs, 4-pin	547888	NEBV-M12G8-KD-3-M12G4
Setpoint module		Technical data → Internet: mpz	
	Setpoint module for generating 6 + 1 analogue voltage signals	546224	MPZ-1-24DC-SGH-6-SW5

Product Range and Company Overview

A Complete Suite and Company Overview

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drivers



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 16,000 employees in 60 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.




© Copyright 2013, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmental friendly printing plant.

Festo North America



**1 Festo Canada
Headquarters
Festo Inc.**
5300 Explorer Drive
Mississauga, ON
L4W 5G4

2 Montréal
5600, Trans-Canada
Pointe-Claire, QC
H9R 1B6

3 Québec City
2930, rue Watt#117
Québec, QC
G1X 4G3



**4 Festo United States
Headquarters
Festo Corporation**
395 Moreland Road
Hauppauge, NY
11788

5 Appleton
North 922 Tower View Drive, Suite N
Greenville, WI
54942

7 Detroit
1441 West Long Lake Road
Troy, MI
48098

6 Chicago
85 W Algonquin - Suite 340
Arlington Heights, IL
60005

8 Silicon Valley
4935 Southfront Road, Suite F
Livermore, CA
94550

Festo Regional Contact Center

Canadian Customers

Commercial Support:
Tel: 1 877 GO FESTO (1 877 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: festo.canada@ca.festo.com

Technical Support:
Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 877 FX FESTO (1 877 393 3786)
Email: technical.support@ca.festo.com

USA Customers

Commercial Support:
Tel: 1 800 99 FESTO (1 800 993 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: customer.service@us.festo.com

Technical Support:
Tel: 1 866 GO FESTO (1 866 463 3786)
Fax: 1 800 96 FESTO (1 800 963 3786)
Email: product.support@us.festo.com