

## Standards-based valves to ISO 5599-1

FESTO



Festo core product range  
Covers 80% of your automation tasks


Worldwide:  
Superb:  
Easy:

Always in stock  
Festo quality at an attractive price  
Simplified procurement and warehousing

★ Generally ready for dispatch from the factory within 24 hours  
In stock at 13 Service Centres worldwide  
More than 2200 products  
★ Generally ready for dispatch from the factory within 5 days  
Assembled for you at 4 Service Centres worldwide  
Up to  $6 \times 10^{12}$  variants per product family

Just look  
for the  
star!


## Characteristics



Innovative	Versatile	Reliable	Easy to install
<ul style="list-style-type: none"><li>High-performance valves in a sturdy metal housing</li><li>Individual electrical connection via square plug sockets or centrally for each valve via round plug sockets</li><li>Valve replacement under pressure possible using vertical pressure shut-off plate</li><li>Reverse operation</li><li>Vacuum operation</li></ul>	<ul style="list-style-type: none"><li>Modular system offering a range of configuration options</li><li>Conversions and extensions are possible at any time</li><li>Integration of innovative function modules possible<ul style="list-style-type: none"><li>Pressure regulator plate</li><li>Throttle plate</li><li>Vertical pressure shut-off plate</li><li>Vertical supply plate</li></ul></li><li>Vertical supply plates permit a flexible air supply and variable pressure zones</li><li>Wide range of valve functions</li><li>Extensive operating voltage range from 12 V DC to 230 V AC</li></ul>	<ul style="list-style-type: none"><li>Sturdy and durable metal components<ul style="list-style-type: none"><li>Valves</li><li>Horizontally linked sub-bases</li><li>Vertically stacked sub-bases</li></ul></li><li>Fast troubleshooting thanks to LED in the plug socket or illuminating seal</li><li>LED integrated in the valve with the round plug variant</li><li>Convenient servicing thanks to valves that can be replaced quickly and easily</li><li>Manual override</li><li>Durable thanks to the use of tried-and-tested piston spool valves</li></ul>	<ul style="list-style-type: none"><li>Plug-in pressure gauges on the pressure regulator plate</li></ul>

## Characteristics

### Simple valve manifold assembly



- [1] Pilot valve with port pattern to ISO 15218
- [2] Various voltages
- [3] Armature tube for plug-on solenoid coils
- [4] End plate
- [5] Manifold sub-base
- [6] Various valve functions
- [7] Cover plate for vacant/expansion position
- [8] Signal status display via LED
- [9] 3-pin round plug
- [10] Manual override

### Equipment options

#### 2x 2/2-way valve, single solenoid

- Normally closed
- Normally closed,  
vacuum operation possible  
at port 3 and 5

#### Operation with external pilot air supply

- For vacuum applications
- For working pressures lower than 3 bar
- For significant pressure fluctuations in the power unit. Power unit and pneumatic control unit are isolated
- For heavily lubricated air in the power unit
- For manifold assemblies where the pressure zones are created via ducts 3 and 5 (not possible with 2x 3/2-way valves)
- For manifold assemblies or pressure zones that are equipped with reversible 2x 3/2-way valves (valves on request)

#### 2x 3/2-way valve, single solenoid

- Normally open
- Normally closed
- 1x normally open, 1x normally closed
- Reverse operation possible

#### Operation with internal pilot air supply

- For small pressure fluctuations in the power unit
- For using pressure regulator plates with vertical stacking, also in reverse operation
- As a low-cost solution

#### 5/2-way valve

- Single solenoid, mechanical or pneumatic spring return
- Double solenoid
- Double solenoid, with dominant signal at port 14

#### Reverse operation with compressed air supply via ducts 3 and 5


- Pressure zone separation via ducts 3 and 5
  - Example: duct 3 vacuum, duct 5 ejector pulse
  - Example: duct 3 high pressure for advancing the piston rod of a double-acting cylinder. Duct 5 low pressure for retracting the piston rod with low energy consumption
- 2x 3/2-way valves used as 5/4-way valve with controllable overlap and pressure zone separation with the reversible variant

#### 5/3-way valve

- Mid-position pressurised
- Mid-position closed
- Mid-position exhausted
- Reversible pressure regulator combined with a reversible 2x 3/2-way valve
  - AB regulator for each of outputs 2 and 4
  - A regulator for output 4
  - B regulator for output 2
- Reversible pressure regulators are in the control position immediately after the power supply is switched on
  - Adjustment possible at all times
  - Dynamic response characteristics
  - Reduced regulator load because the supply pressure is maintained when the valve is switched
  - Not exhausted via the regulator

## Characteristics

### Valve manifold assembly with vertical stacking



- [1] Solenoid valve with individual pilot valves and port pattern to ISO 15218, can be connected using square plug sockets
- [2] Solenoid valve with central round plug
- [3] Throttle plate for adjusting the speed of the drive
- [4] Vertical supply plate as separate compressed air supply for a valve
- [5] Vertical pressure shut-off plate for replacing solenoid valves during operation
- [6] Pressure regulator for adjusting the force of the actuated drive

### Vertical stacking function

#### Pressure regulator

- Single variant to regulate the pressure in duct 4 or 2 or 1 at the valve
- Dual variant to regulate the pressure in ducts 4 and 2 individually
- As reversible version with internally replaced ducts 1 and 3/5
- With pressure gauge connection

#### Throttle plate

- Designed with two throttle valves, at which the exhaust air flow rate at ducts 5 or 3 can be adjusted.
- The movement of the drive is initiated and the required speed is set via the throttle plate using the manual override on the valve.


#### Vertical pressure shut-off plate

- Equipped with a switch via which the compressed air supply can be shut off. As a result, components mounted on the vertical pressure shut-off plate (e.g. a valve) can be replaced without switching off the overall air supply.
- If the control chain has a redundant connection, the cycle can continue even in the case of a cyclical control system.

#### Vertical supply plate


- As additional air supply for a valve
- Separates the valve from duct 1 of the manifold sub-base
- To supply an additional pressure zone

### Individual connection with square plug



The directional control valve has a pilot control to ISO 15218. The solenoid coil plugged onto the armature tube can be chosen in different designs and operating voltages.


### Individual connection with central round plug



The electrical connection is established via a standardised M12 plug, 24 V DC (EN 61076-2-101).


## Characteristics

### Pressure regulator with one regulated duct




- For pressure regulation at the supply input duct 1. The set pressure is identical for ducts 2 and 4
- For pressure regulation at working port duct 4
  - The pressure regulator for reverse operation is supplied via duct 1 of the manifold sub-base and supplies duct 5 on the valve
  - The valve is exhausted via duct 1 to ducts 3 and 5 of the manifold sub-base
- For pressure regulation at working port duct 2
  - In reverse operation duct 3 is supplied here

### Pressure regulator with 2 regulated ducts




- For pressure regulation at working ports ducts 4 and 2
- The pressure regulators for reverse operation are supplied via duct 1 of the manifold sub-base and supply ducts 5 and 3 on the valve
- The directional control valve is exhausted via duct 1 to ducts 3 and 5 of the manifold sub-base.

### Vertical supply plate




- As intermediate supply
  - For one valve
  - To supply an additional pressure zone
- Can be equipped with a valve

### Throttle plate



- Exhaust air flow control valves in ducts 3 and 5
- The throttle plates act as supply-air flow control for pressure zones that are created via ducts 3 and 5

### Vertical pressure shut-off plate



- A switch activated with a slotted screwdriver shuts off duct 1:
- The throttle plates, pressure regulators or valves positioned above it can be replaced
  - Other components of the control chain such as drives, for example, can be replaced following venting via the valve


### Pressure gauge



Plugs into the pressure regulators

## Characteristics

### Port pattern on sub-base to ISO 5599-1



### Sub-base port designations

Duct	Function	Description
[14]	Control unit	Pilot air supply for pilot valves 12 and 14
[5]	Power unit	Exhaust port
[4]	Power unit	Working port
[1]	Power unit	Working air supply port
[2]	Power unit	Working port
[3]	Power unit	Exhaust port
[12]	Control unit	Exhaust port for pilot air supply

## Characteristics

### Pilot air supply

The pneumatic supply ports are located on the right and left end plates and on supply plates.

The ports differ for the following types of pilot air supply:

- Internal pilot air supply
- External pilot air supply

The port for the external pilot air supply is on the right and left end plates. Internal pilot air supply takes place in the valve itself and the ports for pilot air supply are not provided on the end plates.

#### Note

If a gradual pressure build-up is required in the system by using a soft-start valve, then external pilot air should be selected whereby the pilot pressure is already applied at the point of switch-on.

### Internal pilot air supply

Internal pilot air supply can be selected if the working pressure is between 2 and 10 bar, 3 and 10 bar, 2 and 16 bar or 3 and 16 bar, depending on the valve.


In this case the pilot air supply is branched from the compressed air supply 1 using an internal connection in the valve.

### External pilot air supply

If the supply pressure is less than 2 or 3 bar, respectively, you must operate your VSVA valve manifold assembly using external pilot air supply.

The pilot air supply is then supplied via ports 12 and 14 on the end plates.

### Using the seals with ducted/unducted pilot exhaust air



- [1] Ducted pilot air exhaust
- [2] Turning the seal by 180°
- [3] Unducted pilot air exhaust (as supplied)

VSVA valve manifold assemblies have unducted pilot air exhaust. By turning the seal between the valve and manifold block, exhaust air (pilot air) can thus be ducted and silenced (see illustration).

## Characteristics

Pilot air supply via end plates		Description
<b>Left end plate (graphical illustration)</b>		
		<p>Internal pilot air supply</p> <ul style="list-style-type: none"> <li>Pilot air supply is branched within the valve from port 1</li> <li>Port 12 is not available</li> <li>Port 14 is not available</li> <li>Exhaust air via ports 3 and 5</li> <li>Pilot exhaust air via port 12</li> </ul>
		<p>External pilot air supply</p> <ul style="list-style-type: none"> <li>Pilot air supply via ports 12 and 14</li> <li>Exhaust air via ports 3 and 5</li> <li>Unducted pilot exhaust air</li> </ul>
		<p>External pilot air supply, ducted pilot exhaust air</p> <ul style="list-style-type: none"> <li>Pilot air supply via port 14</li> <li>Exhaust air via ports 3 and 5</li> <li>Pilot exhaust air via port 12</li> <li>For valves with central plug M12, 3-pin</li> </ul>
<b>Right end plate (graphical illustration)</b>		
		<p>Internal pilot air supply</p> <ul style="list-style-type: none"> <li>Pilot air supply is branched within the valve from port 1</li> <li>Port 12 is not available</li> <li>Port 14 is not available</li> <li>Exhaust air via ports 3 and 5</li> <li>Pilot exhaust air via port 12</li> </ul>
		<p>External pilot air supply</p> <ul style="list-style-type: none"> <li>Pilot air supply via ports 12 and 14</li> <li>Exhaust air via ports 3 and 5</li> <li>Unducted pilot exhaust air</li> </ul>
		<p>External pilot air supply, ducted pilot exhaust air</p> <ul style="list-style-type: none"> <li>Pilot air supply via port 14</li> <li>Exhaust air via ports 3 and 5</li> <li>Pilot exhaust air via port 12</li> <li>For valves with central plug M12, 3-pin</li> </ul>

## Characteristics

### Creating pressure zones and separating exhaust air


The valve manifold assembly VSVA offers a number of options for creating pressure zones if different working pressures are required.

Pressure zones are created by isolating the internal supply ducts between the manifold sub-bases by appropriate duct separation.

Compressed air is supplied and exhausted via the end plates and supply plates. The position of the supply plates and duct separations can be freely selected.

Duct separations are integrated ex-works as per your order.

Duct separations can be distinguished by their coding, even when the valve manifold assembly is assembled.




### Creating pressure zones

#### Separating seal

Coding	Example image	Coding	Basic representation	Description
			<pre> 3 ─── T 5 ─── T 12 ─── 14 ─── 1 ─── T </pre>	<p>Duct 1 separated</p> <ul style="list-style-type: none"> <li>• Different supply pressure for each pressure zone</li> <li>• Supply pressure for each pressure zone can be switched off separately</li> </ul>
			<pre> 3 ─── 5 ─── 12 ─── 14 ─── 1 ─── T </pre>	<p>Duct 3 and 5 separated</p> <ul style="list-style-type: none"> <li>• The valves (for different pressure zones) do not affect each other via the exhaust ducts</li> </ul>
			<pre> 3 ─── 5 ─── 12 ─── T 14 ─── T 1 ─── T </pre>	<p>Duct 12 and 14 separated</p> <ul style="list-style-type: none"> <li>• Different pilot pressure for each supply zone</li> <li>• Operation with internal and external pilot air supply possible according to pressure zone</li> <li>• Pilot pressure for each pressure zone can be switched off separately</li> </ul>
			<pre> 3 ─── T 5 ─── T 12 ─── 14 ─── 1 ─── T </pre>	<p>Duct 1, 3 and 5 separated</p> <ul style="list-style-type: none"> <li>• Different supply pressure for each pressure zone</li> <li>• The valves (for different pressure zones) do not affect each other via the exhaust ducts</li> <li>• Supply pressure for each pressure zone can be switched off separately</li> </ul>
			<pre> 3 ─── T 5 ─── T 12 ─── T 14 ─── T 1 ─── T </pre>	<p>Ducts 1, 3, 5, 12 and 14 separated</p> <ul style="list-style-type: none"> <li>• Different supply pressure for each pressure zone</li> <li>• Supply pressure for each pressure zone can be switched off separately</li> <li>• The valves (for different pressure zones) do not affect each other via the exhaust ducts</li> <li>• Different pilot pressure for each supply zone</li> <li>• Operation with internal and external pilot air supply possible according to pressure zone</li> <li>• Pilot pressure for each pressure zone can be switched off separately</li> </ul>

## Characteristics

### Examples: Creating pressure zones



[1] Pressure zone separation in ducts 1, 3 and 5. Pressure supply and exhausting via the respective end plate for each of the two pressure zones. Pilot air is supplied jointly via the left end plate.

#### Potential benefit:

- Two different supply pressures
- The valves do not affect each other via the exhaust ducts

[2] Pressure zone separation in ducts 3 and 5. The pressure for both pressure zones is supplied jointly via the end plates. Exhausting for each of the two pressure zones takes place separately via the respective end plate. Pilot air is supplied jointly via the left end plate.

#### Potential benefit:

- The valves do not affect each other via the exhaust ducts

[3] Pressure zone separation in duct 1. Pressure supply via the respective end plate for each of the two pressure zones. Both pressure zones are exhausted jointly via the end plates. Pilot air supplied jointly via the left end plate.






#### Potential benefit:

- Two different supply pressures






## Characteristics

Use of 2x 3/2-way valve as 5/4-way valve																			
Code	Symbol	Table of values	Equivalent circuit symbol	Function															
K		<table border="1"> <thead> <tr> <th>Y1</th> <th>Y2</th> <th>A</th> </tr> </thead> <tbody> <tr> <td>0</td> <td>0</td> <td></td> </tr> <tr> <td>0</td> <td>1</td> <td></td> </tr> <tr> <td>1</td> <td>0</td> <td></td> </tr> <tr> <td>1</td> <td>1</td> <td></td> </tr> </tbody> </table>	Y1	Y2	A	0	0		0	1		1	0		1	1			<ul style="list-style-type: none"> <li>• Normally exhausted</li> <li>• The double-acting drive connected to ducts 2 and 4 is unpressurised when the valve is in the normal position and can be moved by an external force</li> <li>• If there is a signal at Y1(14) and Y2(12), there is pressure at ducts 2 and 4</li> </ul>
Y1	Y2	A																	
0	0																		
0	1																		
1	0																		
1	1																		
		<table border="1"> <thead> <tr> <th>Y1</th> <th>Y2</th> <th>A</th> </tr> </thead> <tbody> <tr> <td>0</td> <td>0</td> <td></td> </tr> <tr> <td>0</td> <td>1</td> <td></td> </tr> <tr> <td>1</td> <td>0</td> <td></td> </tr> <tr> <td>1</td> <td>1</td> <td></td> </tr> </tbody> </table>	Y1	Y2	A	0	0		0	1		1	0		1	1			<ul style="list-style-type: none"> <li>• Normally closed (by combining valve code K and two delockable check valves)</li> <li>• The delockable check valves connected to ducts 2 and 4 are unpressurised when the valve is in the normal position and the pressures in the drive close the check valves leak-tight</li> <li>• The drive remains stationary when the forces are balanced</li> <li>• Leakages can only occur via the drive seals</li> <li>• If there is a signal at Y1(14) and Y2(12), the pressure at ducts 2 and 4 is the same</li> </ul>
Y1	Y2	A																	
0	0																		
0	1																		
1	0																		
1	1																		
N		<table border="1"> <thead> <tr> <th>Y1</th> <th>Y2</th> <th>A</th> </tr> </thead> <tbody> <tr> <td>0</td> <td>0</td> <td></td> </tr> <tr> <td>0</td> <td>1</td> <td></td> </tr> <tr> <td>1</td> <td>0</td> <td></td> </tr> <tr> <td>1</td> <td>1</td> <td></td> </tr> </tbody> </table>	Y1	Y2	A	0	0		0	1		1	0		1	1			<ul style="list-style-type: none"> <li>• Normally open</li> <li>• The double-acting drive connected to ducts 2 and 4 is supplied with the same pressure at both ends when the valve is in the normal position and remains stationary when the forces are balanced</li> <li>• If there is a signal at Y1(10) and Y2(10), ducts 2 and 4 are exhausted, the drive is unpressurised and can be moved by an external force</li> </ul>
Y1	Y2	A																	
0	0																		
0	1																		
1	0																		
1	1																		
H		<table border="1"> <thead> <tr> <th>Y1</th> <th>Y2</th> <th>A</th> </tr> </thead> <tbody> <tr> <td>0</td> <td>0</td> <td></td> </tr> <tr> <td>0</td> <td>1</td> <td></td> </tr> <tr> <td>1</td> <td>0</td> <td></td> </tr> <tr> <td>1</td> <td>1</td> <td></td> </tr> </tbody> </table>	Y1	Y2	A	0	0		0	1		1	0		1	1			<ul style="list-style-type: none"> <li>• Normally open to duct 2</li> <li>• The double-acting drive connected to ducts 2 and 4 is supplied with pressure via duct 2 when the valve is in the normal position. Duct 4 is exhausted. When the system is in its initial position, the drive is thus in a clearly defined position, as would also be the case with a 5/2-way single solenoid valve</li> <li>• If there is a signal at Y1(14) and Y2(10), duct 2 is exhausted and there is pressure at duct 4. The drive leaves the initial position</li> <li>• A closed circuit can be created with this 2x 3/2-way valve by combining it with piloted check valves. However, this is then selected by an active signal at Y2(10).</li> </ul>
Y1	Y2	A																	
0	0																		
0	1																		
1	0																		
1	1																		








## Product range overview

Function	Type	Valve function	Flow rate Valve [l/min]	Operating voltage	→ Page/ Internet
Width 42 mm	<b>Valve with armature tube for solenoid coil MSN</b>				
Working line G1/4		<b>MN1H-5/2</b>	5/2-way valve, single solenoid	1200	12 V DC, 24 V DC, 24 VAC, 110 V AC, 230 V AC
		<b>JMN1</b>	5/2-way valve, double solenoid	1200	
		<b>MN1H-5/3</b>	5/3-way solenoid valve, mid-position valve	1200	
<b>Valve with armature tube for solenoid coil MSF</b>					
		<b>MFH-5/2</b>	5/2-way valve, single solenoid	1200	12 V DC, 24 V DC, 42 V DC, 24 V AC, 42 V AC, 48 V AC, 110 V AC, 120 V AC, 230 V AC, 240 V AC
		<b>JMF</b>	5/2-way valve, double solenoid	1200	
		<b>MFH-5/3</b>	5/3-way solenoid valve, mid-position valve	1200	
<b>Valve with central plug M12, 3-pin</b>					
		<b>VSVA-B-T22</b>	2x 2/2-way valve, single solenoid	1300	24 V DC
		<b>VSVA-B-T32</b>	2x 3/2-way valve, single solenoid	1100	
		<b>VSVA-B-M52</b>	5/2-way valve, single solenoid	1300	
		<b>VSVA-B-B52</b>	5/2-way valve, double solenoid	1300	
		<b>VSVA-B-D52</b>	5/2-way valve, double solenoid	1300	
		<b>VSVA-B-P53</b>	5/3-way solenoid valve, mid-position valve	1300	
<b>Valve with individual plug M12</b>					
		<b>MDH-5/2</b>	5/2-way valve, single solenoid	1200	24 V DC, 42 V AC, 110 V AC, 230 V AC
		<b>JMD</b>	5/2-way valve, double solenoid	1200	
		<b>MDH-5/3</b>	5/3-way solenoid valve, mid-position valve	1200	
<b>Pneumatic valve</b>					
		<b>VL-5/2</b>	5/2-way pneumatic valve, monostable	1200	-
		<b>J</b>	5/2-way pneumatic valve, bistable	1200	
		<b>VL-5/3</b>	5/3-way pneumatic valve, mid-position valve	1200	

## Product range overview

Function	Type	Valve function	Flow rate Valve [l/min]	Operating voltage	→ Page/ Internet
<b>Width 52 mm</b>					
<b>Working line G3/8</b>	<b>Valve with armature tube for solenoid coil MSN</b>				
		<b>MN1H-5/2</b>	5/2-way valve, single solenoid	2300	12 V DC, 24 V DC, 24 VAC, 110 V AC, 230 V AC
		<b>JMN1</b>	5/2-way valve, double solenoid	2300	
		<b>MN1H-5/3</b>	5/3-way solenoid valve, mid-position valve	2300	
	<b>Valve with armature tube for solenoid coil MSF</b>				
		<b>MFH-5/2</b>	5/2-way valve, single solenoid	2300	12 V DC, 24 V DC, 42 V DC, 24 V AC, 42 V AC, 48 V AC, 110 V AC, 120 V AC, 230 V AC, 240 V AC
		<b>JMF</b>	5/2-way valve, double solenoid	2300	
		<b>MFH-5/3</b>	5/3-way solenoid valve, mid-position valve	2300	
	<b>Valve with central plug M12, 3-pin</b>				
		<b>VSVA-B-T22</b>	2x 2/2-way valve, single solenoid	2800	24 V DC
		<b>VSVA-B-T32</b>	2x 3/2-way valve, single solenoid	2200	
		<b>VSVA-B-M52</b>	5/2-way valve, single solenoid	2800	
		<b>VSVA-B-B52</b>	5/2-way valve, double solenoid	2800	
		<b>VSVA-B-D52</b>	5/2-way valve, double solenoid	2800	
		<b>VSVA-B-P53</b>	5/3-way solenoid valve, mid-position valve	2700	
	<b>Valve with individual plug M12</b>				
		<b>MDH-5/2</b>	5/2-way valve, single solenoid	2300	24 V DC, 42 V AC, 110 V AC, 230 V AC
		<b>JMD</b>	5/2-way valve, double solenoid	2300	
		<b>MDH-5/3</b>	5/3-way solenoid valve, mid-position valve	2300	
<b>Pneumatic valve</b>					
		<b>VL-5/2</b>	5/2-way pneumatic valve, monostable	2300	-
		<b>J</b>	5/2-way pneumatic valve, bistable	2300	
		<b>VL-5/3</b>	5/3-way pneumatic valve, mid-position valve	2300	

## Product range overview

Function	Type	Valve function	Flow rate Valve [l/min]	Operating voltage	→ Page/ Internet
<b>Width 65 mm</b>					
<b>Working line G1/2</b>	<b>Valve with armature tube for solenoid coil MSN</b>		<b>MN1H-5/2</b> <b>JMN1</b> <b>MN1H-5/3</b>	5/2-way valve, single solenoid 5/2-way valve, double solenoid 5/3-way solenoid valve, mid-position valve	4500 4500 4000 12 V DC, 24 V DC, 24 VAC, 110 V AC, 230 V AC 30
	<b>Valve with armature tube for solenoid coil MSF</b>		<b>MFH-5/2</b> <b>JMF</b> <b>MFH-5/3</b>	5/2-way valve, single solenoid 5/2-way valve, double solenoid 5/3-way solenoid valve, mid-position valve	4500 4500 4000 12 V DC, 24 V DC, 42 V DC, 24 V AC, 42 V AC, 48 V AC, 110 V AC, 120 V AC, 230 V AC, 240 V AC 42
	<b>Valve with central plug M12, 4-pin</b>		<b>MEBH-5/2</b> <b>JMEB</b> <b>MEBH-5/3</b>	5/2-way valve, single solenoid 5/2-way valve, double solenoid 5/3-way solenoid valve, mid-position valve	4500 4500 4000 24 V DC 57
<b>Working line G1/2</b>	<b>Valve with individual plug M12</b>		<b>MDH-5/2</b> <b>JMD</b> <b>MDH-5/3</b>	5/2-way valve, single solenoid 5/2-way valve, double solenoid 5/3-way solenoid valve, mid-position valve	4500 4500 4000 24 V DC, 42 V AC, 110 V AC, 230 V AC 69
	<b>Pneumatic valve</b>		<b>VL-5/2</b> <b>J</b> <b>VL-5/3</b>	5/2-way pneumatic valve, monostable 5/2-way pneumatic valve, bistable 5/3-way pneumatic valve, mid-position valve	4500 4500 4100 - 90
	<b>Width 76 mm</b>				
<b>Working line G3/4</b>	<b>Valve with individual plug M12</b>		<b>MDH-5/2</b> <b>JMD</b> <b>MDH-5/3</b>	5/2-way valve, single solenoid 5/2-way valve, double solenoid 5/3-way solenoid valve, mid-position valve	6000 6000 4800 24 V DC, 42 V AC, 110 V AC, 230 V AC 73
	<b>Pneumatic valve</b>		<b>VL-5/2</b> <b>J</b> <b>VL-5/3</b>	5/2-way pneumatic valve, monostable 5/2-way pneumatic valve, bistable 5/3-way pneumatic valve, mid-position valve	6000 6000 4800 - 94

## Type codes for valves with round plug


<b>001</b>	<b>Series</b>	
<b>VSPA</b>	Standards-based valve to ISO 5599-1	
<b>002</b>	<b>Directional control valve type</b>	
<b>B</b>	Sub-base valve	
<b>003</b>	<b>Valve function</b>	
<b>T22C</b>	2x2/2-way valve, normally closed	
<b>T32U</b>	2x3/2-way valve, normally open	
<b>T32F</b>	2x3/2-way valve, normally open, reversible	
<b>T32C</b>	2x3/2-way valve, normally closed	
<b>T32N</b>	2x3/2-way valve, normally closed, reversible	
<b>T32H</b>	2x3/2-way valve, 1x normally closed, 1x normally open	
<b>T32W</b>	2x3/2-way valve, 1x normally closed, 1x normally open, reversible	
<b>M52</b>	5/2-way valve, single solenoid/monostable	
<b>B52</b>	5/2-way valve, double solenoid/bistable	
<b>D52</b>	5/2-way valve, double solenoid/bistable, dominant signal	
<b>P53U</b>	5/3-way valve, mid-position pressurised	
<b>P53E</b>	5/3-way valve, mid-position exhausted	
<b>P53C</b>	5/3-way valve, mid-position closed	
<b>004</b>	<b>Reset method for monostable/single solenoid valves</b>	
	None	
<b>A</b>	Pneumatic spring	
<b>M</b>	Mechanical spring	

<b>005</b>	<b>Pilot air</b>	
	Internal	
<b>Z</b>	External	
<b>006</b>	<b>Manual override</b>	
<b>H</b>	Non-detenting	
<b>D</b>	Non-detenting, detenting	
<b>007</b>	<b>Pneumatic connection</b>	
<b>A2</b>	18 mm (02) ISO 15407-1/-2	
<b>A1</b>	26 mm (01) ISO 15407-1/-2	
<b>D1</b>	42 mm (1) ISO 5599-1/-2	
<b>D2</b>	52 mm (2) ISO 5599-1/-2	
<b>008</b>	<b>Nominal operating voltage</b>	
<b>1</b>	24 V DC	
<b>009</b>	<b>Electrical connection</b>	
<b>R2</b>	Central connector M8	
<b>R5</b>	Central plug M12	
<b>010</b>	<b>Display</b>	
<b>L</b>	LED	


## Peripherals overview

### Valve on individual sub-base

Solenoid valve with solenoid coil MSN1



Solenoid valve with central plug M12, 3-pin



### Individual components

	Type	Brief description	→ Page/ Internet	
[1]	Solenoid valve	MN1H-...	Solenoid valve with solenoid coil, port pattern to ISO 5599-1, corresponding solenoid coils → page 139	22
	Solenoid valve	VSVA-...	Solenoid valve with central plug M12, 3-pin, port pattern to ISO 5599-1	46
[2]	Sub-base	VABS-S1-...	Pneumatic connections at the side	97
	Individual sub-base	NAS-...	Pneumatic connections at the side	97
		NAU-...	Pneumatic connections underneath	100
[3]	Silencers	U-...	For mounting in exhaust ports	silencer
[4]	Push-in fitting	QS-...	For connecting compressed air tubing with standard O.D.	qs
[5]	Connecting cable	KMC-..., NEBV-...	Without LED	130
[6]	Connecting cable	KMC-..., NEBV-...	With LED	130
[7]	Plug socket	MSSD-...	For self-assembly	130
[8]	Illuminating seal	M...-LD	For displaying the signal status	130
[9]	Manual override	AHB-...	Tool for detenting manual override	131
[10]	Connecting cable	NEBU-...	–	131
[11]	Plug socket	SIE-...	For self-assembly	131


### Valve variants

MN1H, JMN1H, MFH, JMFH

VSVA


MEBH, JMEBH

MDH, JMDH



## Peripherals overview

### Accessories




### Individual components

	Type	Brief description	→ Page/ Internet
[1]	Silencers	U-...	For mounting in exhaust ports
[2]	Push-in fitting	QS-...	For connecting compressed air tubing with standard O.D.
[3]	Pressure gauge	PAGN-...	With push-in connector
[4]	Connecting cable	KMC-..., NEBV-...	Without LED
[5]	Connecting cable	KMC-...LED, NEBV-...	With LED
[6]	Illuminating seal	M...-LD	For displaying the signal status
[7]	Socket	MSSD-C-M16	With screw terminal connection
[8]	Socket	MSSD-CS-M16	With insulation displacement connection
[9]	Connecting cable	NEBU-...	Angled socket, M12x1, 5-pin,
[10]	Socket	SIE-...	For self-assembly
[11]	Connecting cable	NEBU-...	Straight socket, M12x1, 5-pin
[12]	Blanking plug	B-...	For sealing unused connections

## System overview

### Manifold assembly




## System overview

Individual components		Type	Brief description	→ Seite/ Internet
[1]	Solenoid valve	MN1H-...	With armature tube for solenoid coil MSN1	22
		JMN1H-...	With armature tube for solenoid coil MSN1	22
		JMN1DH-...	With armature tube for solenoid coil MSN1	22
		MFH-...	With armature tube for solenoid coil MSF	34
		JMFH-...	With armature tube for solenoid coil MSF	34
		JMFDH-...	With armature tube for solenoid coil MSF	34
		VSVA-...	With central plug M12, 3-pin	46
		MEBH-...	With central plug M12, 4-pin	57
		JMEBH-...	With central plug M12, 4-pin	57
		JMEBDH-...	With central plug M12, 4-pin	57
		MDH-...	With solenoid coil MD with round plug M12x1	61
		JMDH-...	With solenoid coil MD with round plug M12x1	61
		JMDDH-...	With solenoid coil MD with round plug M12x1	61
		Pneumatic valve	VL-...	Port pattern to ISO 5599-1
			J-...	Port pattern to ISO 5599-1
			JD-...	Port pattern to ISO 5599-1
[2]	Cover plate	NDV-...	For sealing unused manifold sub-bases	112
[3]	Throttle plate	VABF-S1-...-F1B1-C	Controls the flow of exhaust air in ducts 3 and 5	116
		GRO-ZP-...	Controls the flow of exhaust air in ducts 3 and 5	116
[4]	Vertical supply plate	VABF-S1-...-P1A3-G38	Alternative compressed air supply for port 1 of the mounted valve	119
[5]	Vertical pressure shut-off plate	VABF-S1-...-L1D1-C	For blocking duct 1 and duct 14 upstream of a valve	121
[6]	Regulator plate	VABF-S1-...-R...	Pressure regulator for manually setting a particular pressure in the regulated port upstream or downstream of the valve	123
		LR-ZP-...	Pressure regulator for manually setting a particular pressure in the regulated port upstream or downstream of the valve	123
[7]	End plate	VABE-S1-...	With ports for air supply 1 and exhausts 3 and 5 and pilot air supply 12 and 14	109
[8]	Manifold sub-base	VABV-S1-...	With ports 2 and 4 underneath	102
[9]	Duct separation	VABD-S1-1-...	For sealing ducts 1, 3, 5, 12 and 14 between the end plate and the manifold sub-base, e.g. to create pressure zones	113
[10]	Supply plate	VABF-S1-1-...	With ports for air supply 1 and exhausts 3 and 5	104

## System overview

### Manifold assembly




## System overview

Individual components		Type	Brief description	→ Seite/ Internet
[1]	Solenoid valve	MN1H-...	With armature tube for solenoid coil MSN1	22
		JMN1H-...	With armature tube for solenoid coil MSN1	22
		JMN1DH-...	With armature tube for solenoid coil MSN1	22
		MFH-...	With armature tube for solenoid coil MSF	34
		JMFH-...	With armature tube for solenoid coil MSF	34
		JMFDH-...	With armature tube for solenoid coil MSF	34
		VSVA-...	With central plug M12, 3-pin	46
		MEBH-...	With central plug M12, 4-pin	57
		JMEBH-...	With central plug M12, 4-pin	57
		JMEBDH-...	With central plug M12, 4-pin	57
		MDH-...	With solenoid coil MD with round plug M12x1	61
		JMDH-...	With solenoid coil MD with round plug M12x1	61
		JMDDH-...	With solenoid coil MD with round plug M12x1	61
	Pneumatic valve	VL-...	Port pattern to ISO 5599-1	80
		J-...	Port pattern to ISO 5599-1	80
		JD-...	Port pattern to ISO 5599-1	80
[2]	Cover plate	NDV-...	For sealing unused manifold sub-bases	112
[3]	Throttle plate	VABF-S1-...-F1B1-C	Controls the flow of exhaust air in ducts 3 and 5	116
		GRO-ZP-...	Controls the flow of exhaust air in ducts 3 and 5	116
[4]	Vertical supply plate	VABF-S1-...-P1A3-G38	Alternative compressed air supply for port 1 of the mounted valve	119
[5]	Vertical pressure shut-off plate	VABF-S1-...-L1D1-C	For blocking duct 1 and duct 14 upstream of a valve	121
[6]	Regulator plate	VABF-S1-...-R...	Pressure regulator for manually setting a particular pressure in the regulated port upstream or downstream of the valve	123
		LR-ZP-...	Pressure regulator for manually setting a particular pressure in the regulated port upstream or downstream of the valve	123
[7]	End plate kit	NEV-...	With ports for air supply 1 and exhausts 3 and 5	108
[8]	Manifold sub-base	NAV-...	With ports 2 and 4 underneath	102
[9]	Isolating disc	NSC-...	For sealing ducts 1, 3, 5 between end plate and manifold sub-base, e.g. to create pressure zones	112

## Data sheet – Width 42 mm

-  - Flow rate  
1200 l/min



## General technical data

Design	Piston spool valve		
Sealing principle	Soft		
Actuation type	Electric		
Type of control	Piloted		
Flow direction	With external pilot air supply	Reversible	
	With internal pilot air supply	Non-reversible	
Exhaust air function	Can be throttled		
Manual override	Non-detenting, detenting via accessory		
Type of mounting	On sub-base, via through-hole		
Mounting position	Any		
Nominal width	[mm]	8	
Overlap	Positive overlap		
Width	[mm]	42	
Grid dimension	[mm]	43	
Pneumatic connections	Sub-base, size 1 to ISO 5599-1		
Noise level	[dB (A)]	85	
Conforms to standard	ISO 5599-1		
Certification	With internal pilot air supply	c UL us - Recognized (OL)	
Maritime classification <sup>1)</sup>	See certificate		

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

## Flow rates

Valve function	5/2-way valve, single solenoid	5/2-way valve, double solenoid	5/3-way valve
Standard nominal flow rate	[l/min] 1200		

## Switching times [ms]

		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way valve, single solenoid	MN1H-5/2-D-1-C	23	32	–	–
	MN1H-5/2-D-1-S-C	23	32	–	–
	MN1H-5/2-D-1-FR-C	17	39	–	–
	MN1H-5/2-D-1-FRS-C	17	39	–	–
5/2-way valve, double solenoid	JMN1H-5/2-D-1-C	–	–	18	–
	JMN1H-5/2-D-1-S-C	–	–	18	–
	JMN1DH-5/2-D-1-C	–	–	18	15
	JMN1DH-5/2-D-1-S-C	–	–	18	15
5/3-way valve	MN1H-5/3G-D-1-C	20	44	–	–
	MN1H-5/3G-D-1-S-C	20	44	–	–
	MN1H-5/3E-D-1-C	20	46	–	–
	MN1H-5/3E-D-1-S-C	20	46	–	–
	MN1H-5/3B-D-1-C	20	46	–	–
	MN1H-5/3B-D-1-S-C	20	46	–	–

## Technical data – Width 42 mm

<b>Operating and environmental conditions</b>		Pneumatic spring	Mechanical spring
Reset method			
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	Internal pilot air supply	[bar]	2 ... 10
	External pilot air supply	[bar]	-0.9 ... +16
Pilot pressure		[bar]	2 ... 10
Ambient temperature		[°C]	-5 ... +50
Temperature of medium		[°C]	-5 ... +50

<b>Safety characteristics</b>		
Max. positive test pulse with 0 signal	[μs]	3700
Max. negative test pulse on 1 signal	[μs]	4600
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance		Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6

<b>Electrical data</b>	
Electrical connection	Via N1 coil, to be ordered separately
Degree of protection to EN 60529	IP65


<b>Materials</b>	
Housing	Die-cast aluminium
Seals	HNBR, NBR
Note on materials	RoHS-compliant

## Technical data – Width 42 mm

### Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)


5/2-way valves, single solenoid



- [2] Manual override
- [3] Captive retaining screws
- [4] Slot for inscription label

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
MN1H-5/2- ...	42	28	6	30	M5	M5	106	74	38	9	46.5	15.3	117.5	87.6	43.8	36	18	89
MN1H-5/2- ... -FR- ...													128	98				










5/2-way double solenoid valves, 5/3-way valves



- [2] Manual override
- [3] Captive retaining screws
- [4] Slot for inscription label

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
JMN1H-5/2- ...	42	28	6	30	M5	M5	106	74	38	9	46.5	15.3	147.3	87.6	43.8	36	18	89
JMN1DH-5/2- ...														87.6				
MN1H-5/3...																108.4		


## Ordering data – Width 42 mm

Ordering data – Valves with armature tube for solenoid coil MSN1 <sup>1)</sup>		Pilot air supply	Weight [g]	Part no.	Type
<b>5/2-way valve, single solenoid</b>					
	Pneumatic spring reset method	Internal	450	159688	MN1H-5/2-D-1-C
	Pneumatic spring reset method	External	450	159686	MN1H-5/2-D-1-S-C
	Mechanical spring reset method	Internal	450	159687	MN1H-5/2-D-1-FR-C
	Mechanical spring reset method	External	450	159716	MN1H-5/2-D-1-FR-S-C
<b>5/2-way valve, double solenoid</b>					
	-	Internal	610	159690	JMN1H-5/2-D-1-C
	-	External	610	159689	JMN1H-5/2-D-1-S-C
	With dominant signal at 14	Internal	610	159691	JMN1DH-5/2-D-1-C
	With dominant signal at 14	External	610	159717	JMN1DH-5/2-D-1-S-C
<b>5/3-way valve</b>					
	Normally closed, mechanical spring reset method	Internal	650	159681	MN1H-5/3G-D-1-C
	Normally closed, mechanical spring reset method	External	650	159680	MN1H-5/3G-D-1-S-C
	Normally exhausted, mechanical spring reset method	Internal	650	159683	MN1H-5/3E-D-1-C
	Normally exhausted, mechanical spring reset method	External	650	159682	MN1H-5/3E-D-1-S-C
	Normally open, mechanical spring reset method	Internal	650	159685	MN1H-5/3B-D-1-C
	Normally open, mechanical spring reset method	External	650	159684	MN1H-5/3B-D-1-S-C

1) Solenoid coils → page 129

## Data sheet – Width 52 mm

-  - Flow rate  
2300 l/min



## General technical data

Design	Piston spool valve		
Sealing principle	Soft		
Actuation type	Electric		
Type of control	Piloted		
Flow direction	With external pilot air supply	Reversible	
	With internal pilot air supply	Non-reversible	
Exhaust air function	Can be throttled		
Manual override	Non-detenting, detenting via accessory		
Type of mounting	On sub-base, with through-hole and screw		
Mounting position	Any		
Nominal width	[mm]	11.5	
Overlap	Positive overlap		
Width	[mm]	52	
Grid dimension	[mm]	56	
Pneumatic connections	Sub-base, size 2 to ISO 5599-1		
Noise level	[dB (A)]	85	
Conforms to standard	ISO 5599-1		
Certification	With internal pilot air supply	c UL us - Recognized (OL)	
Maritime classification <sup>1)</sup>	See certificate		

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

Flow rates	5/2-way valve, single solenoid	5/2-way valve, double solenoid	5/3-way valve
Valve function			
Standard nominal flow rate	[l/min]	2300	

Switching times [ms]		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way valve, single solenoid	MN1H-5/2-D-2-C	46	69	–	–
	MN1H-5/2-D-2S-C	43	62	–	–
	MN1H-5/2-D-2-FR-C	24	62	–	–
	MN1H-5/2-D-2-FRS-C	24	62	–	–
5/2-way valve, double solenoid	JMN1H-5/2-D-2-C	–	–	21	–
	JMN1H-5/2-D-2S-C	–	–	21	–
	JMN1DH-5/2-D-2-C	–	–	24	21
	JMN1DH-5/2-D-2S-C	–	–	24	21
5/3-way valve	MN1H-5/3G-D-2-C	33	82	–	–
	MN1H-5/3G-D-2S-C	33	82	–	–
	MN1H-5/3E-D-2-C	36	84	–	–
	MN1H-5/3E-D-2S-C	36	84	–	–
	MN1H-5/3B-D-2-C	35	78	–	–
	MN1H-5/3B-D-2S-C	35	78	–	–

## Technical data – Width 52 mm


<b>Operating and environmental conditions</b>					
Reset method	Pneumatic spring	Mechanical spring			
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]				
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]				
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)				
Operating pressure	Internal pilot air supply External pilot air supply	[bar] [bar]	2 ... 10 -0.9 ... +16 2 ... 10 -0.9 ... +16		
Pilot pressure		[bar]	3 ... 10		
Ambient temperature		[°C]	-5 ... +50		
Temperature of medium		[°C]	-5 ... +50		
<b>Safety characteristics</b>					
Max. positive test pulse with 0 signal	[μs]	3700			
Max. negative test pulse on 1 signal	[μs]	4600			
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27				
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6				
<b>Electrical data</b>					
Electrical connection	Via N1 coil, to be ordered separately				
Degree of protection to EN 60529	IP65				
<b>Materials</b>					
Housing	Die-cast aluminium				
Seals	HNBR, NBR				
Note on materials	RoHS-compliant				

## Technical data – Width 52 mm

### Dimensions

5/2-way valves, single solenoid

Download CAD data → [www.festo.com](http://www.festo.com)




- [2] Manual override
- [3] Captive retaining screws
- [4] Slot for inscription label

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
MN1H-5/2- ...	54	38	9	30	M6	M5	116	84	48	9.5	56.5	15.3	147.6	123.4	61.7	48	24	98
MN1H-5/2- ... -FR- ...													161.5	140.7				

5/2-way double solenoid valves, 5/3-way valves

- [2] Manual override
- [3] Captive retaining screws
- [4] Slot for inscription label



Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
JMN1H-5/2- ...	54	38	9	30	M6	M5	116	84	48	9.5	56.5	15.3	165	123.4	61.7	48	24	98
JMN1DH-5/2- ...														123.4	61.7			
MN1H-5/3...														158	79			


## Ordering data – Width 52 mm

Ordering data – Valves with armature tube for solenoid coil MSN1 <sup>1)</sup>		Pilot air supply	Weight [g]	Part no.	Type
<b>5/2-way valve, single solenoid</b>					
	Pneumatic spring reset method	Internal	710	159700	MN1H-5/2-D-2-C
	Pneumatic spring reset method	External	710	159698	MN1H-5/2-D-2-S-C
	Mechanical spring reset method	Internal	710	159699	MN1H-5/2-D-2-FR-C
	Mechanical spring reset method	External	710	159718	MN1H-5/2-D-2-FR-S-C
<b>5/2-way valve, double solenoid</b>					
	-	Internal	940	159702	JMN1H-5/2-D-2-C
	-	External	940	159701	JMN1H-5/2-D-2-S-C
	With dominant signal at 14	Internal	940	159703	JMN1DH-5/2-D-2-C
	With dominant signal at 14	External	940	159719	JMN1DH-5/2-D-2-S-C
<b>5/3-way valve</b>					
	Normally closed, mechanical spring reset method	Internal	940	159693	MN1H-5/3G-D-2-C
	Normally closed, mechanical spring reset method	External	940	159692	MN1H-5/3G-D-2-S-C
	Normally exhausted, mechanical spring reset method	Internal	940	159695	MN1H-5/3E-D-2-C
	Normally exhausted, mechanical spring reset method	External	940	159694	MN1H-5/3E-D-2-S-C
	Normally open, mechanical spring reset method	Internal	940	159697	MN1H-5/3B-D-2-C
	Normally open, mechanical spring reset method	External	940	159696	MN1H-5/3B-D-2-S-C

1) Solenoid coils → page 129

## Data sheet – Width 65 mm

-  Flow rate  
4600 l/min

**General technical data**

Design	Piston spool valve		
Sealing principle	Soft		
Actuation type	Electric		
Type of control	Piloted		
Flow direction	With external pilot air supply	Reversible	
	With internal pilot air supply	Non-reversible	
Exhaust air function	Can be throttled		
Manual override	Non-detenting, detenting via accessory		
Type of mounting	On sub-base, with through-hole and screw		
Mounting position	Any		
Nominal width	[mm]	14.5	
Overlap		Positive overlap	
Width	[mm]	65	
Grid dimension	[mm]	71	
Pneumatic connections		Sub-base, size 3 to ISO 5599-1	
Noise level	[dB (A)]	85	
Conforms to standard		ISO 5599-1	
Certification	With internal pilot air supply	c UL us - Recognized (OL)	
Maritime classification <sup>1)</sup>		See certificate	

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

**Flow rates**

Valve function		5/2-way valve	5/3-way valve		
		Normally closed	Normally exhausted	Normally open	
Standard nominal flow rate	[l/min]	4500	4100	4600	4000

## Technical data – Width 65 mm


Switching times [ms]		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way valve, single solenoid	MN1H-5/2-D-3-C	49	71	–	–
	MN1H-5/2-D-3-S-C	49	71	–	–
	MN1H-5/2-D-3-FR-C	33	74	–	–
	MN1H-5/2-D-3-FRS-C	33	74	–	–
5/2-way valve, double solenoid	JMN1H-5/2-D-3-C	–	–	21	–
	JMN1H-5/2-D-3-S-C	–	–	21	–
	JMN1DH-5/2-D-3-C	–	–	24	21
	JMN1DH-5/2-D-3-S-C	–	–	24	21
5/3-way valve	MN1H-5/3G-D-3-C	33	82	–	–
	MN1H-5/3G-D-3-S-C	33	82	–	–
	MN1H-5/3E-D-3-C	36	84	–	–
	MN1H-5/3E-D-3-S-C	36	84	–	–
	MN1H-5/3B-D-3-C	35	78	–	–
	MN1H-5/3B-D-3-S-C	35	78	–	–
Operating and environmental conditions					
Reset method		Pneumatic spring		Mechanical spring	
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]			
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]			
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)			
Operating pressure	Internal pilot air supply	[bar]	2 ... 10	3 ... 10	
	External pilot air supply	[bar]	-0.9 ... +16	-0.9 ... +16	
Pilot pressure	[bar]	2 ... 10	3 ... 10		
Ambient temperature	[°C]	-5 ... +50			
Temperature of medium	[°C]	-5 ... +50			
Safety characteristics					
Max. positive test pulse with 0 signal	[μs]	3700			
Max. negative test pulse on 1 signal	[μs]	4600			
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27			
Vibration resistance		Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6			
Electrical data					
Electrical connection		Via N1 coil, to be ordered separately			
Degree of protection to EN 60529		IP65			
Materials					
Housing		Die-cast aluminium			
Seals		HNBR, NBR			
Note on materials		RoHS-compliant			

## Technical data – Width 65 mm

### Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)


5/2-way valves, single solenoid



- [2] Manual override
- [3] Captive retaining screws
- [4] Slot for inscription label

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
MN1H-5/2- ...	65	48	12	30	M8	M5	123	87.3	55	12	63.5	15.3	169	145.4	72.7	64	32	109
MN1H-5/2- ... -FR- ...													184.8	164.7				













5/2-way double solenoid valves, 5/3-way valves



- [2] Manual override
- [3] Captive retaining screws
- [4] Slot for inscription label

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
JMN1H-5/2- ...	65	48	12	30	M8	M5	123	87.3	55	12	-	15.3	185.7	145.4	72.7	64	32	109
JMN1DH-5/2- ...											-			145.4	72.7			
MN1H-5/3...											63.5			184	92			


## Ordering data – Width 65 mm

Ordering data – Valves with armature tube for solenoid coil MSN1 <sup>1)</sup>		Pilot air supply	Weight [g]	Part no.	Type
<b>5/2-way valve, single solenoid</b>					
	Pneumatic spring reset method	Internal	1000	<b>159712</b>	MN1H-5/2-D-3-C
	Pneumatic spring reset method	External	1000	<b>159710</b>	MN1H-5/2-D-3-S-C
	Mechanical spring reset method	Internal	1000	<b>159711</b>	MN1H-5/2-D-3-FR-C
	Mechanical spring reset method	External	1000	<b>160896</b>	MN1H-5/2-D-3-FR-S-C
<b>5/2-way valve, double solenoid</b>					
	-	Internal	1090	<b>159714</b>	JMN1H-5/2-D-3-C
	-	External	1090	<b>159713</b>	JMN1H-5/2-D-3-S-C
	With dominant signal at 14	Internal	1090	<b>159715</b>	JMN1DH-5/2-D-3-C
	With dominant signal at 14	External	1090	<b>160897</b>	JMN1DH-5/2-D-3-S-C
<b>5/3-way valve</b>					
	Normally closed, mechanical spring reset method	Internal	1170	<b>159705</b>	MN1H-5/3G-D-3-C
	Normally closed, mechanical spring reset method	External	1170	<b>159704</b>	MN1H-5/3G-D-3-S-C
	Normally exhausted, mechanical spring reset method	Internal	1170	<b>159707</b>	MN1H-5/3E-D-3-C
	Normally exhausted, mechanical spring reset method	External	1170	<b>159706</b>	MN1H-5/3E-D-3-S-C
	Normally open, mechanical spring reset method	Internal	1170	<b>159709</b>	MN1H-5/3B-D-3-C
	Normally open, mechanical spring reset method	External	1170	<b>159708</b>	MN1H-5/3B-D-3-S-C

1) Solenoid coils → page 129

## Data sheet – Width 42 mm

-  - Flow rate  
1200 l/min



General technical data		
Type	MFH- ... -C, JMF- ... -C	MFH- ... -EX, JMF- ... -EX
Design	Piston spool valve	Piston spool valve
Sealing principle	Soft	Soft
Actuation type	Electric	Electric
Type of control	Piloted	Piloted
Flow direction	With external pilot air supply With internal pilot air supply	Reversible Non-reversible
Exhaust air function	Can be throttled	Can be throttled
Manual override	Non-detenting, detenting via accessory	Non-detenting, detenting via accessory
Type of mounting	On sub-base, via through-hole	
Mounting position	Any	Any
Nominal width [mm]	8	8
Overlap	Positive overlap	
Width [mm]	42	42
Grid dimension [mm]	43	43
Pneumatic connections	Sub-base, size 1 to ISO 5599-1	
Noise level [dB (A)]	85	85
Conforms to standard	ISO 5599-1	ISO 5599-1
Maritime classification <sup>1)</sup>	See certificate	–

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

Flow rates			
Valve function	5/2-way valve, single solenoid	5/2-way valve, double solenoid	5/3-way valve
Standard nominal flow rate [l/min]	1200		

Switching times [ms]		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way valve, single solenoid	MFH-5/2...	23	35	–	–
	MFH-5/2-D-1-FR...	16	45	–	–
5/2-way valve, double solenoid	JMFH...	–	–	16	–
	JMFDH...	–	–	16	13
5/3-way valve	MFH-5/3G-D-1-C	18	35	–	–
	MFH-5/3G-D-1-C-EX	18	35	–	–
	MFH-5/3G-D-1-S-C	18	36	–	–
	MFH-5/3G-D-1-S-C-EX	18	36	–	–
	MFH-5/3E-D-1-C	18	36	–	–
	MFH-5/3E-D-1-C-EX	18	36	–	–
	MFH-5/3E-D-1-S-C	18	36	–	–
	MFH-5/3E-D-1-S-C-EX	18	36	–	–
	MFH-5/3B-D-1-C	18	36	–	–
	MFH-5/3B-D-1-C-EX	18	36	–	–
	MFH-5/3B-D-1-S-C	18	36	–	–
	MFH-5/3B-D-1-S-C-EX	18	36	–	–

## Technical data – Width 42 mm



<b>ATEX</b>					
Type	MFH- ... -EX, JMFH- ... -EX, JMFDH- ... -EX				
ATEX category for gas	II 2G				
Type of ignition protection for gas	Ex h IIC T4 Gb				
ATEX category for dust	II 2D				
Type of ignition protection for dust	Ex h IIIC T105°C Db				
Explosion-proof ambient temperature	[°C]	-5 ≤ Ta ≤ +40			
CE marking (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)				
<b>Operating and environmental conditions</b>					
Reset method	Pneumatic spring	Mechanical spring			
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]				
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]				
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)				
Operating pressure	Internal pilot air supply External pilot air supply	[bar]	2 ... 10 -0.9 ... +16		
Pilot pressure	[bar]	2 ... 10	3 ... 10		
Ambient temperature	[°C]	-5 ... +40			
Temperature of medium	[°C]	-10 ... +60			
	[°C]	-5 ... +40 (MFH- ... -EX, JMFH- ... -EX, JMFDH- ... -EX)			
<b>Safety characteristics</b>					
Max. positive test pulse with 0 signal	[μs]	2200			
Max. negative test pulse on 1 signal	[μs]	3700			
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27				
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6				
<b>Electrical data</b>					
Electrical connection	Via F coil, to be ordered separately				
Degree of protection to EN 60529	IP65				
<b>Materials</b>					
Housing	Die-cast aluminium				
Seals	HNBR, NBR				
Note on materials	RoHS-compliant				

## Technical data – Width 42 mm

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

5/2-way valves, single solenoid





- [2] Manual override
- [3] Captive retaining screws
- [4] Slot for inscription label

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
MFH-5/2- ...	42	28	6	30	M5	M5	100	70.3	38	9	46.5	13.5	115	87.6	43.8	36	18	89
MFH-5/2- ... -FR- ...													125.6	98				













5/2-way double solenoid valves, 5/3-way valves

- [2] Manual override
- [3] Captive retaining screws
- [4] Slot for inscription label



Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
JMFH-5/2- ...	42	28	6	30	M5	M5	100	70.3	38	9	-	13.5	142.6	87.6	43.8	36	18	89
JMFDH-5/2- ...													87.6	43.8				
MFH-5/3...													108.4	54.2				


## Ordering data – Width 42 mm

Ordering data – Valves with armature tube for solenoid coil MSF <sup>1)</sup>		Description	Pilot air supply	Weight [g]		Part no.	Type
<b>5/2-way valve, single solenoid</b>							
	Pneumatic spring reset method	Internal	390	–	150981	MFH-5/2-D-1-C	
				ATEX category → page 35	535954	MFH-5/2-D-1-C-EX	
	Pneumatic spring reset method	External	390	–	152562	MFH-5/2-D-1-S-C	
				ATEX category → page 35	535957	MFH-5/2-D-1-S-C-EX	
	Mechanical spring reset method	Internal	390	–	151016	MFH-5/2-D-1-FR-C	
				ATEX category → page 35	535960	MFH-5/2-D-1-FR-C-EX	
	Mechanical spring reset method	External	390	–	188510	MFH-5/2-D-1-FR-S-C	
<b>5/2-way valve, double solenoid</b>							
	–	Internal	490	–	150980	JMFH-5/2-D-1-C	
				ATEX category → page 35	535963	JMFH-5/2-D-1-C-EX	
	–	External	490	–	152563	JMFH-5/2-D-1-S-C	
				ATEX category → page 35	535966	JMFH-5/2-D-1-S-C-EX	
	With dominant signal at 14	Internal	490	–	151019	JMFH-5/2-D-1-C	
				ATEX category → page 35	536071	JMFH-5/2-D-1-C-EX	
<b>5/3-way valve</b>							
	Normally closed, mechanical spring reset method	Internal	520	–	150982	MFH-5/3G-D-1-C	
				ATEX category → page 35	535969	MFH-5/3G-D-1-C-EX	
	Normally closed, mechanical spring reset method	External	520	–	152564	MFH-5/3G-D-1-S-C	
				ATEX category → page 35	535972	MFH-5/3G-D-1-S-C-EX	
	Normally exhausted, mechanical spring reset method	Internal	520	–	150983	MFH-5/3E-D-1-C	
				ATEX category → page 35	535975	MFH-5/3E-D-1-C-EX	
	Normally exhausted, mechanical spring reset method	External	520	–	152565	MFH-5/3E-D-1-S-C	
				ATEX category → page 35	535978	MFH-5/3E-D-1-S-C-EX	
	Normally open, mechanical spring reset method	Internal	520	–	150984	MFH-5/3B-D-1-C	
				ATEX category → page 35	535981	MFH-5/3B-D-1-C-EX	
	Normally open, mechanical spring reset method	External	520	–	152566	MFH-5/3B-D-1-S-C	
				ATEX category → page 35	535984	MFH-5/3B-D-1-S-C-EX	

1) Solenoid coils → page 129

## Data sheet – Width 52 mm

-  Flow rate  
2300 l/min



General technical data		
Type	MFH- ... -C, JMF- ... -C	MFH- ... -EX, JMF- ... -EX
Design	Piston spool valve	Piston spool valve
Sealing principle	Soft	Soft
Actuation type	Electric	Electric
Type of control	Piloted	Piloted
Flow direction	With external pilot air supply With internal pilot air supply	Reversible Non-reversible
Exhaust air function	Can be throttled	Can be throttled
Manual override	Non-detenting, detenting via accessory	Non-detenting, detenting via accessory
Type of mounting	On sub-base, with through-hole and screw	
Mounting position	Any	Any
Nominal width [mm]	11.5	11.5
Overlap	Positive overlap	Positive overlap
Width [mm]	52	52
Grid dimension [mm]	56	56
Pneumatic connections	Sub-base, size 2 to ISO 5599-1	
Noise level [dB (A)]	85	85
Conforms to standard	ISO 5599-1	ISO 5599-1
Maritime classification <sup>1)</sup>	See certificate	–

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

Flow rates			
Valve function	5/2-way valve, single solenoid	5/2-way valve, double solenoid	5/3-way valve
Standard nominal flow rate [l/min]	2300		

Switching times [ms]		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way valve, single solenoid	MFH-5/2...	48	71	–	–
	MFH-5/2-D-2-FR...	27	73	–	–
5/2-way valve, double solenoid	JMFH...	–	–	18	–
	JMFDH...	–	–	18	18
5/3-way valve	MFH-5/3G...	33	63	–	–
	MFH-5/3E...	35	67	–	–
	MFH-5/3B...	35	69	–	–

ATEX	
Type	MFH- ... -EX, JMFH- ... -EX, JMFDH- ... -EX
ATEX category for gas	II 2G
Type of ignition protection for gas	Ex h IIC T4 Gb
ATEX category for dust	II 2D
Type of ignition protection for dust	Ex h IIIC T105°C Db
Explosion-proof ambient temperature [°C]	–5 ≤ Ta ≤ +40
CE marking (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)

## Technical data – Width 52 mm

<b>Operating and environmental conditions</b>		Pneumatic spring	Mechanical spring
Reset method			
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	Internal pilot air supply	[bar]	2 ... 10
Operating pressure	External pilot air supply	[bar]	-0.9 ... +16
Pilot pressure		[bar]	2 ... 10
Ambient temperature		[°C]	-5 ... +40
Temperature of medium		[°C]	-10 ... +60

<b>Safety characteristics</b>			
Max. positive test pulse with 0 signal		[μs]	2200
Max. negative test pulse on 1 signal		[μs]	3700
Shock resistance			Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance			Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6

<b>Electrical data</b>			
Electrical connection			Via F coil, to be ordered separately
Degree of protection to EN 60529			IP65


<b>Materials</b>			
Housing			Die-cast aluminium
Seals			HNBR, NBR
Note on materials			RoHS-compliant

## Technical data – Width 52 mm

### Dimensions

5/2-way valves, single solenoid


Download CAD data → [www.festo.com](http://www.festo.com)



Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
MFH-5/2- ...	54	38	9	30	M6	M5	110	80.3	48	9.5	56.5	13.5	142	123.4	61.7	48	24	98
MFH-5/2- ... -FR- ...													159.4	140.7				











5/2-way double solenoid valves, 5/3-way valves

[2] Manual override  
[3] Captive retaining screws  
[4] Slot for inscription label



Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
JMFH-5/2- ...	54	38	9	30	M6	M5	110	80.3	48	9.5	-	13.5	160.4	123.4	61.7	48	24	97
JMFDH-5/2- ...													160.4	123.4	61.7			97
MFH-5/2...													160	158	79			98


## Ordering data – Width 52 mm

Ordering data – Valves with armature tube for solenoid coil MSF <sup>1)</sup>						
Circuit symbol	Description	Pilot air supply	Weight [g]		Part no.	Type
<b>5/2-way valve, single solenoid</b>						
	Pneumatic spring reset method	Internal	650	–	151851	MFH-5/2-D-2-C
	ATEX category → page 38			–	535955	MFH-5/2-D-2-C-EX
	Pneumatic spring reset method	External	650	–	151022	MFH-5/2-D-2-S-C
	ATEX category → page 38			–	535958	MFH-5/2-D-2-S-C-EX
	Mechanical spring reset method	Internal	650	–	151709	MFH-5/2-D-2-FR-C
	ATEX category → page 38			–	535961	MFH-5/2-D-2-FR-C-EX
<b>5/2-way valve, double solenoid</b>						
	–	Internal	820	–	151852	JMFH-5/2-D-2-C
	ATEX category → page 38			–	535964	JMFH-5/2-D-2-C-EX
	–	External	820	–	151023	JMFH-5/2-D-2-S-C
	ATEX category → page 38			–	535967	JMFH-5/2-D-2-S-C-EX
	With dominant signal at 14	Internal	820	–	151853	JMFH-5/2-D-2-C
	ATEX category → page 38			–	536072	JMFH-5/2-D-2-C-EX
<b>5/3-way valve</b>						
	Normally closed, mechanical spring reset method	Internal	820	–	151854	MFH-5/3G-D-2-C
	ATEX category → page 38			–	535970	MFH-5/3G-D-2-C-EX
	Normally closed, mechanical spring reset method	External	820	–	151024	MFH-5/3G-D-2-S-C
	ATEX category → page 38			–	535973	MFH-5/3G-D-2-S-C-EX
	Normally exhausted, mechanical spring reset method	Internal	820	–	151855	MFH-5/3E-D-2-C
	ATEX category → page 38			–	535976	MFH-5/3E-D-2-C-EX
	Normally exhausted, mechanical spring reset method	External	820	–	151025	MFH-5/3E-D-2-S-C
	ATEX category → page 38			–	535979	MFH-5/3E-D-2-S-C-EX
	Normally open, mechanical spring reset method	Internal	820	–	151856	MFH-5/3B-D-2-C
	ATEX category → page 38			–	535982	MFH-5/3B-D-2-C-EX
	Normally open, mechanical spring reset method	External	820	–	151026	MFH-5/3B-D-2-S-C
	ATEX category → page 38			–	535985	MFH-5/3B-D-2-S-C-EX

1) Solenoid coils → page 129

## Data sheet – Width 65 mm

-  Flow rate  
Up to 4600 l/min



General technical data		
Type	MFH- ... -C, JMF- ... -C	MFH- ... -EX, JMF- ... -EX
Design	Piston spool valve	Piston spool valve
Sealing principle	Soft	Soft
Actuation type	Electric	Electric
Type of control	Piloted	Piloted
Flow direction	With external pilot air supply With internal pilot air supply	Reversible Non-reversible
Exhaust air function		Can be throttled
Manual override		Non-detenting, detenting via accessory
Type of mounting		On sub-base, with through-hole and screw
Mounting position	Any	Any
Nominal width	[mm]	14.5
Overlap		Positive overlap
Width	[mm]	65
Grid dimension	[mm]	71
Pneumatic connections		Sub-base, size 3 to ISO 5599-1
Noise level	[dB (A)]	85
Conforms to standard		ISO 5599-1
Maritime classification <sup>1)</sup>	See certificate	–

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

Flow rates		5/2-way valve	5/3-way valve		
Valve function		Normally closed	Normally exhausted	Normally open	
Standard nominal flow rate	[l/min]	4500	4100	4600	4000
<b>Switching times [ms]</b>					
		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way valve, single solenoid	MFH-5/2...	60	66	–	–
	MFH-5/2-D-1-FR...	28	79	–	–
5/2-way valve, double solenoid	JMFH...	–	–	18	–
	JMFDH...	–	–	18	18
5/3-way valve	MFH-5/3G...	36	77	–	–
	MFH-5/3E...	37	78	–	–
	MFH-5/3B...	36	75	–	–

## Technical data – Width 65 mm



<b>ATEX</b>					
Type	MFH- ... -EX, JMFH- ... -EX, JMFDH- ... -EX				
ATEX category for gas	II 2G				
Type of ignition protection for gas	Ex h IIC T4 Gb				
ATEX category for dust	II 2D				
Type of ignition protection for dust	Ex h IIIC T105°C Db				
Explosion-proof ambient temperature	[°C]	-5 ≤ Ta ≤ +40			
CE marking (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)				
<b>Operating and environmental conditions</b>					
Reset method	Pneumatic spring	Mechanical spring			
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]				
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]				
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)				
Operating pressure	Internal pilot air supply External pilot air supply	[bar]	2 ... 10 -0.9 ... +16		
Pilot pressure	[bar]	2 ... 10	3 ... 10		
Ambient temperature	[°C]	-5 ... +40			
Temperature of medium	[°C]	-10 ... +60			
<b>Safety characteristics</b>					
Max. positive test pulse with 0 signal	[μs]	2200			
Max. negative test pulse on 1 signal	[μs]	3700			
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27				
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6				
<b>Electrical data</b>					
Electrical connection	Via F coil, to be ordered separately				
Degree of protection to EN 60529	IP65				
<b>Materials</b>					
Housing	Die-cast aluminium				
Seals	HNBR, NBR				
Note on materials	RoHS-compliant				

## Technical data – Width 65 mm

### Dimensions

5/2-way valves, single solenoid



Download CAD data → [www.festo.com](http://www.festo.com)



Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
MFH-5/2- ...	65	48	12	30	M8	M5	117	87.3	55	12	63.5	13.5	163	145.4	72.7	64	32	109
MFH-5/2- ... -FR- ...													182	164.7				

5/2-way double solenoid valves, 5/3-way valves

[2] Manual override  
[3] Captive retaining screws  
[4] Slot for inscription label



Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6
JMFH-5/2- ...	65	48	12	30	M8	M5	117	87.3	55	12	–	13.5	181	145.4	72.7	64	32	109
JMFDH-5/2- ...													145.4	72.7				
MFH-5/3...													184	92				

## Ordering data – Width 65 mm

Ordering data – Valves with armature tube for solenoid coil MSF <sup>1)</sup>		Description	Pilot air supply	Weight [g]		Part no.	Type
<b>5/2-way valve, single solenoid</b>							
 	Pneumatic spring reset method	Internal	960	–	151870	MFH-5/2-D-3-C	
				ATEX category → page 43	535956	MFH-5/2-D-3-C-EX	
 	Pneumatic spring reset method	External	960	–	151032	MFH-5/2-D-3-S-C	
				ATEX category → page 43	535959	MFH-5/2-D-3-S-C-EX	
 	Mechanical spring reset method	Internal	960	–	151711	MFH-5/2-D-3-FR-C	
				ATEX category → page 43	535962	MFH-5/2-D-3-FR-C-EX	
<b>5/2-way valve, double solenoid</b>							
 	–	Internal	1060	–	151871	JMFH-5/2-D-3-C	
				ATEX category → page 43	535965	JMFH-5/2-D-3-C-EX	
 	–	External	1060	–	151033	JMFH-5/2-D-3-S-C	
				ATEX category → page 43	535968	JMFH-5/2-D-3-S-C-EX	
 	With dominant signal at 14	Internal	1060	–	151872	JMFH-5/2-D-3-C	
				ATEX category → page 43	536073	JMFH-5/2-D-3-C-EX	
<b>5/3-way valve</b>							
 	Normally closed, mechanical spring reset method	Internal	1040	–	151873	MFH-5/3G-D-3-C	
				ATEX category → page 43	535971	MFH-5/3G-D-3-C-EX	
 	Normally closed, mechanical spring reset method	External	1040	–	151034	MFH-5/3G-D-3-S-C	
				ATEX category → page 43	535974	MFH-5/3G-D-3-S-C-EX	
 	Normally exhausted, mechanical spring reset method	Internal	1040	–	151874	MFH-5/3E-D-3-C	
				ATEX category → page 43	535977	MFH-5/3E-D-3-C-EX	
 	Normally exhausted, mechanical spring reset method	External	1040	–	151035	MFH-5/3E-D-3-S-C	
				ATEX category → page 43	535980	MFH-5/3E-D-3-S-C-EX	
 	Normally open, mechanical spring reset method	Internal	1040	–	151875	MFH-5/3B-D-3-C	
				ATEX category → page 43	535983	MFH-5/3B-D-3-C-EX	
 	Normally open, mechanical spring reset method	External	1040	–	151036	MFH-5/3B-D-3-S-C	
				ATEX category → page 43	535986	MFH-5/3B-D-3-S-C-EX	

1) Solenoid coils → page 129

## Data sheet – Width 42 mm

-  - Flow rate  
Up to 1300 l/min

-  - Voltage  
24 V DC



### General technical data

Design	Piston spool valve						
Sealing principle	Soft						
Actuation type	Electric						
Type of control	Piloted						
Exhaust air function	Flow control, external or via vertically stacked throttle plate						
Manual override	Non-detenting, detenting						
Type of mounting	On sub-base						
Mounting position	Any						
Nominal width	[mm]	11					
Overlap	Positive overlap						
Width	[mm]	42					
Grid dimension	[mm]	43					
Pneumatic connections	Sub-base, size 1 to ISO 5599-1						
Conforms to standard	ISO 5599-1						
Certification	c CSA us (OL) c UL us - Recognized (OL)						

### Flow rates

Valve function	2/2-way valve	3/2-way valve	5/2-way valve	5/3-way valve
Standard nominal flow rate [l/min]	1300	1100	1300	1300
Valve	1600	1600	2000	1900
Valve on individual sub-base	1400	1200	1400	1400
Valve pneumatically interlinked	1300	1100	1300	1400

### Switching times [ms]

		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
2x 2/2-way valve	VSVA-B-T22...	20	38	–	–
2x 3/2-way valve	VSVA-B-T32...	20	38	–	–
2x 3/2-way valve, reversible	VSVA-B-T32...	34	28	–	–
5/2-way valve, single solenoid	VSVA-B-M52-A...	27	45	–	–
	VSVA-B-M52-M...	22	60	–	–
5/2-way valve, double solenoid	VSVA-B-B52...	–	–	16	–
	VSVA-B-D52...	–	–	–	19
5/3-way valve	VSVA-B-P53...	22	65	–	–


## Technical data – Width 42 mm

<b>Operating and environmental conditions</b>					
Valve function	2x 2/2-way valve	2x 3/2-way valve	2x 3/2-way valve, reversible	5/2-way valve	5/3-way valve
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]				
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]				
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)				
Operating pressure	Internal pilot air supply [bar]	3 ... 10	3 ... 10	-	3 ... 10
	External pilot air supply [bar]	3 ... 10	3 ... 10	-0.9 ... +10	-0.9 ... +16
Pilot pressure	[bar]	3 ... 10			
Ambient temperature	[°C]	-5 ... +50			
Relative humidity	[%]	0 ... 90			
<b>Safety characteristics</b>					
Valve function	2x 3/2-way valve	5/2-way valve	5/2-way valve, with dominant signal at 14	5/3-way valve	
Max. positive test pulse with 0 signal	[μs]	1600	1400	1600	1400
Max. negative test pulse on 1 signal	[μs]	1100	900	1100	900
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27				
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6				
<b>Electrical data</b>					
Valve function	2x 2/2-way valve	2x 3/2-way valve	5/2-way valve	5/3-way valve	
Electrical connection	Central plug, round design M12x1, 3-pin				
Signal status display	LED				
Coil characteristics	Voltage [V DC]	24			
	Power [W]	1.3	1.3	1.6	1.6
Permissible voltage fluctuations	[%]	±10			
Duty cycle	[%]	100			
Degree of protection to EN 60529	IP65, NEMA4 (in combination with a plug socket)				
<b>Materials</b>					
Housing	PA				
Seals	NBR, FPM				
Screws	Galvanised steel				
Note on materials	RoHS-compliant				
<b>Product weight</b>					
2x 2/2-way valve	[g]	442			
2x 3/2-way valve	[g]	442			
5/2-way valve, single solenoid	[g]	426			
5/2-way valve, double solenoid	[g]	439			
5/3-way valve	[g]	456			


## Data sheet – Width 42 mm

### Pilot pressure $p_{12/14}$ as a function of working pressure $p_1$

2x 2/2-way valve and 2x 3/2-way valve




5/2-way valve and 5/3-way valve, external pilot air supply




### Protective circuit

Each VSVA solenoid coil is protected with a spark arresting protective circuit as well as against polarity reversal.

### 24 V DC version




### M12x1 – Pin allocation on the valve



- 2 Signal (+) Solenoid 12
- 3 com (-)
- 4 Signal (+) Solenoid 14

### Dimensions



Download CAD data → [www.festo.com](http://www.festo.com)



Type	B1	B2	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5
VSVA-B ....D1-1R5L	42	28	M5	58.3	48	0.25	46.6	55.3	137.8	32	36	18	69.3

## Ordering data – Width 42 mm

## ★ Core product range

Ordering data	Description	Flow direction	Pilot air supply	Part no.	Type
<b>5/2-way valve, single solenoid</b>					
	Pneumatic spring reset method	Non-reversible	Internal	★ 561362	VSVA-B-M52-AD-D1-1R5L
	Mechanical spring reset method	Non-reversible	Internal	★ 561363	VSVA-B-M52-MD-D1-1R5L
<b>5/2-way valve, double solenoid</b>					
	Dominance at 1st signal	Non-reversible	Internal	★ 561364	VSVA-B-B52-D-D1-1R5L

Festo core product range







Generally ready for dispatch from the factory within 24 hours










Generally ready for dispatch from the factory within 5 days

## Ordering data – Width 42 mm

Ordering data	Description	Flow direction	Pilot air supply	Part no.	Type
<b>Circuit symbol</b>					
<b>2x 2/2-way valve</b>	2x normally closed, Pneumatic spring reset method	Non-reversible	Internal	Order via online configurator → Internet: vsva	
	2x normally closed, pneumatic spring reset method	Non-reversible	External		
	2x normally closed, vacuum operation possible at 3 and 5, pneumatic spring reset method	Reversible	Internal		
<b>2x 3/2-way valve</b>					
	2x normally closed, pneumatic spring reset method	Non-reversible	Internal	561359	VSVA-B-T32C-AD-D1-1R5L
	2x normally closed, pneumatic spring reset method	Non-reversible	External	561369	VSVA-B-T32C-AZD-D1-1R5L
	2x normally open, pneumatic spring reset method	Non-reversible	Internal	561360	VSVA-B-T32U-AD-D1-1R5L
	2x normally open, pneumatic spring reset method	Non-reversible	External	561370	VSVA-B-T32U-AZD-D1-1R5L
	1x normally closed, 1x normally open, pneumatic spring reset method	Non-reversible	Internal	561361	VSVA-B-T32H-AD-D1-1R5L
	1x normally closed, 1x normally open, pneumatic spring reset method	Non-reversible	External	561371	VSVA-B-T32H-AZD-D1-1R5L
<b>2x 3/2-way valve, reversible</b>					
	2x normally closed, pneumatic spring reset method	Reversible	External	Order via online configurator → Internet: vsva	
	2x normally open, pneumatic spring reset method	Reversible	External		
	1x normally closed, 1x normally open, pneumatic spring reset method	Reversible	External		


## Ordering data – Width 42 mm

Ordering data	Description	Flow direction	Pilot air supply	Part no.	Type
<b>5/2-way valve, single solenoid</b>					
	Pneumatic spring reset method	Reversible	External	561372	VSVA-B-M52-AZD-D1-1R5L
	Mechanical spring reset method	Reversible	External	561373	VSVA-B-M52-MZD-D1-1R5L
<b>5/2-way valve, double solenoid</b>					
	Dominance at 1st signal	Reversible	External	561374	VSVA-B-B52-ZD-D1-1R5L
	With dominant signal at 14	Non-reversible	Internal	561365	VSVA-B-D52-D-D1-1R5L
	With dominant signal at 14	Reversible	External	561375	VSVA-B-D52-ZD-D1-1R5L
<b>5/3-way valve</b>					
	Normally closed, mechanical spring reset method	Non-reversible	Internal	561366	VSVA-B-P53C-D-D1-1R5L
	Normally closed, mechanical spring reset method	Reversible	External	561376	VSVA-B-P53C-ZD-D1-1R5L
	Normally open, mechanical spring reset method	Non-reversible	Internal	561368	VSVA-B-P53U-D-D1-1R5L
	Normally open, mechanical spring reset method	Reversible	External	561378	VSVA-B-P53U-ZD-D1-1R5L
	Normally exhausted, mechanical spring reset method	Non-reversible	Internal	561367	VSVA-B-P53E-D-D1-1R5L
	Normally exhausted, mechanical spring reset method	Reversible	External	561377	VSVA-B-P53E-ZD-D1-1R5L

## Data sheet – Width 52 mm

-  - Flow rate  
Up to 2800 l/min

-  - Voltage  
24 V DC



### General technical data

Design	Piston spool valve						
Sealing principle	Soft						
Actuation type	Electric						
Type of control	Piloted						
Exhaust air function	Flow control, external or via vertically stacked throttle plate						
Manual override	Non-detenting, detenting						
Type of mounting	On sub-base						
Mounting position	Any						
Nominal width	[mm]	15					
Overlap	Positive overlap						
Width	[mm]	52					
Grid dimension	[mm]	59					
Pneumatic connections	Sub-base, size 2 to ISO 5599-1						
Conforms to standard	ISO 5599-1						
Certification	c CSA us (OL) c UL us - Recognized (OL) C-Tick						

### Flow rates

Valve function		2/2-way valve	3/2-way valve	5/2-way valve	5/3-way valve
Standard nominal flow rate	[l/min]	2800	2200	2800	2700
Valve		4000	3000	4000	3600
Valve on individual sub-base		2400	2000	2400	2300
Valve pneumatically interlinked		2800	2200	2800	2700

### Switching times [ms]

		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
2x 2/2-way valve	VSVA-B-T22...	14	35	-	-
2x 3/2-way valve	VSVA-B-T32...	20	35	-	-
2x 3/2-way valve, reversible	VSVA-B-T32...	30	30	-	-
5/2-way valve, single solenoid	VSVA-B-M52-A...	40	45	-	-
	VSVA-B-M52-M...	20	60	-	-
5/2-way valve, double solenoid	VSVA-B-B52...	-	-	18	-
	VSVA-B-D52...	-	-	-	18
5/3-way valve	VSVA-B-P53...	23	60	-	-

## Technical data – Width 52 mm

<b>Operating and environmental conditions</b>					
Valve function	2x 2/2-way valve	2x 3/2-way valve	2x 3/2-way valve, reversible	5/2-way valve	5/3-way valve
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]				
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]				
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)				
Operating pressure	Internal pilot air supply [bar]	3 ... 10	3 ... 10	-	3 ... 10
	External pilot air supply [bar]	3 ... 10	3 ... 10	-0.9 ... +10	-0.9 ... +16
Pilot pressure	[bar]	3 ... 10			
Ambient temperature	[°C]	-5 ... +50			
Relative humidity	[%]	0 ... 90			

<b>Safety characteristics</b>	
CE marking (see declaration of conformity)	To EU EMC Directive <sup>1)</sup>
KC mark	KC-EMV
Max. positive test pulse with 0 signal	[μs] 1000
Max. negative test pulse on 1 signal	[μs] 3500
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6

1) For information about the area of use, see the EC declaration of conformity at: [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

<b>Electrical data</b>		
Electrical connection		Central plug, round design M12x1, 3-pin
Signal status display		LED
Coil characteristics	Voltage [V DC]	24
	Power [W]	4.6
Permissible voltage fluctuations	[%]	±10
Nominal pick-up current per solenoid coil	[mA]	165
Nominal current with current reduction	[mA]	35
Time until current reduction	[ms]	30
Duty cycle [%]		100
Degree of protection to EN 60529	IP65, NEMA4 (in combination with a plug socket)	


<b>Materials</b>		
Housing		Die-cast aluminium, polyamide
Seals		HNBR, NBR, FPM
Screws		Galvanised steel
Note on materials		RoHS-compliant

<b>Product weight</b>		
2x 2/2-way valve	[g]	740
2x 3/2-way valve	[g]	740
5/2-way valve, single solenoid	[g]	702
5/2-way valve, double solenoid	[g]	732
5/3-way valve	[g]	780


## Data sheet – Width 52 mm

### Pilot pressure $p_{12/14}$ as a function of working pressure $p_1$

2x 2/2-way valve and 2x 3/2-way valve




5/2-way valve and 5/3-way valve, external pilot air supply



### Protective circuit


Each VSVA solenoid coil is protected with a spark arresting protective circuit as well as against polarity reversal.

### 24 V DC version



[1] Holding current reduction


### M12x1 – Pin allocation on the valve



- 2 Signal (+) Solenoid 12
- 3 com (-)
- 4 Signal (+) Solenoid 14

### Dimensions













Download CAD data → [www.festo.com](http://www.festo.com)



## Ordering data – Width 52 mm

Ordering data	Description	Flow direction	Pilot air supply	Part no.	Type
<b>2x 2/2-way valve</b>					
	2x normally closed, pneumatic spring reset method	Non-reversible	Internal	Order via online configurator → Internet: vsva	
	2x normally closed, pneumatic spring reset method	Non-reversible	External		
<b>2x 3/2-way valve</b>					
	2x normally closed, pneumatic spring reset method	Non-reversible	Internal	566990	VSVA-B-T32C-AD-D2-1R5L
	2x normally closed, pneumatic spring reset method	Non-reversible	External	567000	VSVA-B-T32C-AZD-D2-1R5L
	2x normally open, pneumatic spring reset method	Non-reversible	Internal	566991	VSVA-B-T32U-AD-D2-1R5L
	2x normally open, pneumatic spring reset method	Non-reversible	External	567001	VSVA-B-T32U-AZD-D2-1R5L
	1x normally closed, 1x normally open, pneumatic spring reset method	Non-reversible	Internal	566992	VSVA-B-T32H-AD-D2-1R5L
	1x normally closed, 1x normally open, pneumatic spring reset method	Non-reversible	External	567002	VSVA-B-T32H-AZD-D2-1R5L
<b>2x 3/2-way valve, reversible</b>					
	2x normally closed, pneumatic spring reset method	Reversible	External	Order via online configurator → Internet: vsva	
	2x normally open, pneumatic spring reset method	Reversible	External		
	1x normally closed, 1x normally open, pneumatic spring reset method	Reversible	External		


## Ordering data – Width 52 mm

Ordering data	Description	Flow direction	Pilot air supply	Part no.	Type
<b>5/2-way valve, single solenoid</b>					
	Pneumatic spring reset method	Non-reversible	Internal	566993	VSVA-B-M52-AD-D2-1R5L
	Pneumatic spring reset method	Reversible	External	567003	VSVA-B-M52-AZD-D2-1R5L
	Mechanical spring reset method	Non-reversible	Internal	566994	VSVA-B-M52-MD-D2-1R5L
	Mechanical spring reset method	Reversible	External	567004	VSVA-B-M52-MZD-D2-1R5L
<b>5/2-way valve, double solenoid</b>					
	Dominance at 1st signal	Non-reversible	Internal	566995	VSVA-B-B52-D-D2-1R5L
	Dominance at 1st signal	Reversible	External	567005	VSVA-B-B52-ZD-D2-1R5L
	With dominant signal at 14	Non-reversible	Internal	566996	VSVA-B-D52-D-D2-1R5L
	With dominant signal at 14	Reversible	External	567006	VSVA-B-D52-ZD-D2-1R5L
<b>5/3-way valve</b>					
	Normally closed, mechanical spring reset method	Non-reversible	Internal	566997	VSVA-B-P53C-D-D2-1R5L
	Normally closed, mechanical spring reset method	Reversible	External	567007	VSVA-B-P53C-ZD-D2-1R5L
	Normally open, mechanical spring reset method	Non-reversible	Internal	566999	VSVA-B-P53U-D-D2-1R5L
	Normally open, mechanical spring reset method	Reversible	External	567009	VSVA-B-P53U-ZD-D2-1R5L
	Normally exhausted, mechanical spring reset method	Non-reversible	Internal	566998	VSVA-B-P53E-D-D2-1R5L
	Normally exhausted, mechanical spring reset method	Reversible	External	567008	VSVA-B-P53E-ZD-D2-1R5L

## Data sheet – Width 65 mm

-  - Flow rate  
Up to 4600 l/min

-  - Voltage  
24 V DC

**General technical data**

Design	Piston spool valve						
Sealing principle	Soft						
Actuation type	Electric						
Type of control	Piloted						
Flow direction	Non-reversible						
Exhaust air function	Can be throttled						
Manual override	Non-detenting						
Type of mounting	With through-hole						
Mounting position	Any						
Nominal width	[mm]	14.5					
Width	[mm]	65					
Grid dimension	[mm]	71					
Pneumatic connections	Sub-base, size 3 to ISO 5599-1						
Conforms to standard	ISO 5599-1						

**Flow rates**

Valve function	5/2-way valve	5/3-way valve	Normally closed	Normally exhausted	Normally open
Standard nominal flow rate	[l/min]	4500	4100	4600	4000

**Switching times [ms]**

		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way valve, single solenoid	MEBH-5/2...	59	87	–	–
	MEBH-5/2-D-1-ZSR-FR...	28	109	–	–
5/2-way valve, double solenoid	JMEBH...	–	–	16	–
	JMEBDH...	–	–	–	20
5/3-way valve	MEBH-5/3G...	38	130	–	–
	MEBH-5/3E...	38	130	–	–
	MEBH-5/3B...	38	130	–	–


## Technical data – Width 65 mm

Operating and environmental conditions		Pneumatic spring	Mechanical spring
Reset method			
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[bar]	2 ... 10	3 ... 10
Ambient temperature	[°C]	-5 ... +50	
Temperature of medium	[°C]	-5 ... +50	
Relative humidity	[%]	0 ... 90	
Electrical data			
Electrical connection		Central plug, round design M12x1, 4-pin	
Characteristic coil data	Voltage	[V DC]	24
	Power	[W]	2.5
Degree of protection to EN 60529		IP65	
Materials			
Housing		Die-cast aluminium	
Seals		NBR	

## Technical data – Width 65 mm

## Dimensions


5/2-way valves, single solenoid

Download CAD data → [www.festo.com](http://www.festo.com)

- [1] Attachment of plug socket  
adjustable by 3x30°
- [2] Manual override
- [3] Captive retaining screws
- [5] LED display
- [6] Angled plug socket SIE-WD-TR  
→ page 131

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
MEBH-5/2 ...	65	48	12	17.5	M8	M12	130	97.8	55	12	93.1	158.7	145.4	72.7	64	32	86
MEBH-5/2- ... -FR-C												178	164.7				

## 5/2-way double solenoid valves, 5/3-way valves




- [1] Attachment of plug socket  
adjustable by 3x30°
- [2] Manual override
- [3] Captive retaining screws
- [5] LED display
- [6] Angled plug socket SIE-WD-TR  
→ page 131

Type	B1	B2	B3	B4	D1	D2	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
JMEBH-5/2- ...	65	48	12	17.5	M8	M12	130	97.8	55	12	93.1	171.9	145.4	72.7	64	32	86
JMEBDH-5/2- ...												145.4	72.7				
MEBH-5/3...												184	92				

## Ordering data – Width 65 mm


### Central plug M12 – Pin allocation

5/2-way valve, single solenoid



- 1 Unused
- 2 Unused
- 3 com (-)
- 4 Signal (+) Solenoid 14

5/2-way double solenoid valve and 5/3-way valve



- 1 Unused
- 2 Signal (+) Solenoid 12
- 3 com (-)
- 4 Signal (+) Solenoid 14

Ordering data Circuit symbol	Description	Pilot air supply	Weight [g]	Part no.	Type
<b>5/2-way valve, single solenoid</b>					
	Pneumatic spring reset method	Internal	1000	<b>184507</b>	<b>MEBH-5/2-D-3-ZSR-C</b>
	Mechanical spring reset method	Internal	1000	<b>184508</b>	<b>MEBH-5/2-D-3-ZSR-FR-C</b>
<b>5/2-way valve, double solenoid</b>					
	-	Internal	1080	<b>184509</b>	<b>JMEBH-5/2-D-3-ZSR-C</b>
	With dominant signal at 14	Internal	1080	<b>184510</b>	<b>JMEBDH-5/2-D-3-ZSR-C</b>
<b>5/3-way valve</b>					
	Normally closed, mechanical spring reset method	Internal	1120	<b>184512</b>	<b>MEBH-5/3G-D-3-ZSR-C</b>
	Normally exhausted, mechanical spring reset method	Internal	1120	<b>184511</b>	<b>MEBH-5/3E-D-3-ZSR-C</b>
	Normally open, mechanical spring reset method	Internal	1120	<b>184513</b>	<b>MEBH-5/3B-D-3-ZSR-C</b>

## Data sheet – Width 42 mm

-  - Flow rate  
Up to 1200 l/min

-  - Voltage  
24 V DC

**General technical data**

Design	Piston spool valve		
Sealing principle	Soft		
Actuation type	Electric		
Type of control	Piloted		
Flow direction	With external pilot air supply	Reversible	
	With internal pilot air supply	Non-reversible	
Exhaust air function	Can be throttled		
Manual override	Non-detenting		
Type of mounting	On sub-base via through-hole		
Mounting position	Any		
Nominal width	[mm]	8	
Overlap		Positive overlap	
Width	[mm]	42	
Grid dimension	[mm]	43	
Pneumatic connections	Sub-base, size 1 to ISO 5599-1		
Noise level	[dB (A)]	85	
Conforms to standard	ISO 5599-1		

**Flow rates**

Standard nominal flow rate	[l/min]	1200
----------------------------	---------	------

**Switching times [ms]**

		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way valve, single solenoid	MDH-5/2-...	25	36	–	–
	MDH-5/2-...-FR-...	20	42	–	–
5/2-way valve, double solenoid	JMDH-...	–	–	18	–
	JMDDH-...	–	–	18	18
5/3-way valve	MDH-5/3G-...	25	55	–	–
	MDH-5/3E-...	25	55	–	–
	MDH-5/3B-...	25	55	–	–


## Technical data – Width 42 mm

Operating and environmental conditions		Pneumatic spring	Mechanical spring
Reset method			
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	Internal pilot air supply External pilot air supply	[bar] -0.9 ... +16	2 ... 10 3 ... 10 -0.9 ... +16
Pilot pressure	Internal pilot air supply External pilot air supply	[bar] 3 ... 10	2 ... 10 3 ... 10
Ambient temperature		[°C] -10 ... +50	
Temperature of medium		[°C] -10 ... +50	
Safety characteristics			
Max. positive test pulse with 0 signal		[μs]	3800
Max. negative test pulse on 1 signal		[μs]	4900
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27	
Vibration resistance		Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6	
Electrical data			
Electrical connection		M12x1	
Characteristic coil data	Voltage Power	[V DC] [W]	24 2.7
Permissible voltage fluctuations		[%]	±10
Duty cycle		[%]	100
Degree of protection to EN 60529		IP65	
Materials			
Housing		Die-cast aluminium	
Seals		HNBR, NBR	

## Technical data – Width 42 mm

## Dimensions


5/2-way valves, single solenoid

Download CAD data → [www.festo.com](http://www.festo.com)

- [1] Solenoid coil can be repositioned by 90° regardless of the manual override
- [2] Manual override
- [3] Captive retaining screws
- [4] Slot for inscription label
- [5] LED display
- [6] Connection for power supply  
M12x1  
2-pin coil to VDMA  
4-pin coil to Desina

Type	B1	B2	B3	B4	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
MDH-5/2 ...	42	28	6	30	M5	87.2	77.2	38	9	46.5	121.8	87.6	43.8	36	18	-
MDH-5/2- ... -FR...											132.2	98				

5/2-way double solenoid valves, 5/3-way valves




- [1] Solenoid coil can be repositioned by 90° regardless of the manual override
- [2] Manual override
- [3] Captive retaining screws
- [4] Slot for inscription label
- [5] LED display
- [6] Connection for power supply  
M12x1  
2-pin coil to VDMA  
4-pin coil to Desina

Type	B1	B2	B3	B4	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
JMDH-5/2- ...	42	28	6	30	M5	87.2	77.2	38	9	-	148	87.6	43.8	36	18	108.5
JMDDH-5/2- ...											87.6	43.8				
MDH-5/3...											108.4	54.3				

## Ordering data – Width 42 mm


### Pin allocation

M12 plug – 2-pin to VDMA



- 1 Unused
- 2 Unused
- 3 com (-)
- 4 Signal (+)

M12 plug – 4-pin to Desina



- 1 Connected to 2
- 2 Connected to 1
- 3 com (-)
- 4 Signal (+)

### Ordering data – Solenoid valves

Circuit symbol	Description	Coil	Pilot air supply	Weight [g]	Part no.	Type
<b>5/2-way valve, single solenoid</b>						
	Pneumatic spring reset method	2-pin to VDMA 4-pin to Desina	Internal Internal	420 420	197125 540803	MDH-5/2-D-1-M12-C MDH-5/2-D-1-M12D-C
	Pneumatic spring reset method	2-pin to VDMA 4-pin to Desina	External External	420 420	533332 540810	MDH-5/2-D-1-S-M12-C MDH-5/2-D-1-S-M12D-C
	Mechanical spring reset method	2-pin to VDMA 4-pin to Desina	Internal Internal	420 420	533010 540804	MDH-5/2-D-1-FR-M12-C MDH-5/2-D-1-FR-M12D-C
	Mechanical spring reset method	2-pin to VDMA 4-pin to Desina	External External	420 420	533761 540811	MDH-5/2-D-1-S-FR-M12-C MDH-5/2-D-1-S-FR-M12D-C
<b>5/2-way valve, double solenoid</b>						
	-	2-pin to VDMA 4-pin to Desina	Internal Internal	550 550	532687 540809	JMDH-5/2-D-1-M12-C JMDH-5/2-D-1-M12D-C
	With dominant signal at 14	2-pin to VDMA 4-pin to Desina	Internal Internal	550 550	539079 540808	JMDDH-5/2-D-1-M12-C JMDDH-5/2-D-1-M12D-C
<b>5/3-way valve</b>						
	Normally closed, mechanical spring reset method	2-pin to VDMA 4-pin to Desina	Internal Internal	580 580	525307 540806	MDH-5/3G-D-1-M12-C MDH-5/3G-D-1-M12D-C
	Normally exhausted, mechanical spring reset method	2-pin to VDMA 4-pin to Desina	Internal Internal	580 580	197126 540805	MDH-5/3E-D-1-M12-C MDH-5/3E-D-1-M12D-C
	Normally open, mechanical spring reset method	2-pin to VDMA 4-pin to Desina	Internal Internal	580 580	533005 540807	MDH-5/3B-D-1-M12-C MDH-5/3B-D-1-M12D-C

## Data sheet – Width 52 mm

-  - Flow rate  
Up to 2300 l/min

-  - Voltage  
24 V DC

**General technical data**

Design	Piston spool valve		
Sealing principle	Soft		
Actuation type	Electric		
Type of control	Piloted		
Flow direction	Non-reversible		
Exhaust air function	Can be throttled		
Manual override	Non-detenting		
Type of mounting	On sub-base, with through-hole and screw		
Mounting position	Any		
Nominal width	[mm]	11.5	
Overlap	Positive overlap		
Width	[mm]	52	
Grid dimension	[mm]	56	
Pneumatic connections	Sub-base, size 2 to ISO 5599-1		
Noise level	[dB (A)]	85	
Conforms to standard	ISO 5599-1		

**Flow rates**

Standard nominal flow rate	[l/min]	2300
----------------------------	---------	------

**Switching times [ms]**

		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way valve, single solenoid	MDH-5/2...	45	60	–	–
	MDH-5/2-...-FR-...	25	60	–	–
5/2-way valve, double solenoid	JMDH-...	–	–	20	–
	JMDDH-...	–	–	20	20
5/3-way valve	MDH-5/3G...	35	70	–	–
	MDH-5/3E...	35	70	–	–
	MDH-5/3B...	35	70	–	–


## Technical data – Width 52 mm

Operating and environmental conditions		
Reset method	Pneumatic spring	Mechanical spring
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[bar]	2 ... 10
Ambient temperature	[°C]	-10 ... +50
Temperature of medium	[°C]	-10 ... +50
Safety characteristics		
Max. positive test pulse with 0 signal	[μs]	3800
Max. negative test pulse on 1 signal	[μs]	4900
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27	
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6	
Electrical data		
Electrical connection	M12x1	
Characteristic coil data	Voltage Power	[V DC] [W]
Permissible voltage fluctuations	[%]	±10
Duty cycle	[%]	100
Degree of protection to EN 60529	IP65	
Materials		
Housing	Die-cast aluminium	
Seals	HNBR, NBR	
Note on materials	RoHS-compliant	

## Technical data – Width 52 mm

## Dimensions

5/2-way valves, single solenoid


Download CAD data → [www.festo.com](http://www.festo.com)

- [1] Solenoid coil can be repositioned by 90° regardless of the manual override
- [2] Manual override
- [3] Captive retaining screws
- [4] Slot for inscription label
- [5] LED display
- [6] Connection for power supply  
M12x1  
2-pin coil to VDMA  
4-pin coil to Desina

Type	B1	B2	B3	B4	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
MDH-5/2 ...	54	38	9	30	M6	97.2	87.2	48	9.5	56.5	144.6	123.4	61.7	48	24	-
MDH-5/2- ... -FR...											161.9	140.6				

5/2-way double solenoid valves, 5/3-way valves

- [1] Solenoid coil can be repositioned by 90° regardless of the manual override
- [2] Manual override
- [3] Captive retaining screws
- [4] Slot for inscription label
- [5] LED display
- [6] Connection for power supply  
M12x1  
2-pin coil to VDMA  
4-pin coil to Desina




Type	B1	B2	B3	B4	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
JMDH-5/2- ...	54	38	9	30	M6	97.2	87.2	48	9.5	-	165.8	123.4	61.7	48	24	126.3
JMDDH-5/2- ...											123.4	61.7				
MDH-5/3...											158	79				

## Ordering data – Width 52 mm


### Pin allocation

M12 plug – 2-pin to VDMA



- 1 Unused
- 2 Unused
- 3 com (-)
- 4 Signal (+)

M12 plug – 4-pin to Desina



- 1 Connected to 2
- 2 Connected to 1
- 3 com (-)
- 4 Signal (+)

Ordering data	Description	Coil	Pilot air supply	Weight [g]	Part no.	Type
<b>5/2-way valve, single solenoid</b>						
	Pneumatic spring reset method	2-pin to VDMA 4-pin to Desina	Internal Internal	810 810	533008 540812	MDH-5/2-D-2-M12-C MDH-5/2-D-2-M12D-C
	Mechanical spring reset method	2-pin to VDMA 4-pin to Desina	Internal Internal	810 810	533011 540813	MDH-5/2-D-2-FR-M12-C MDH-5/2-D-2-FR-M12D-C
<b>5/2-way valve, double solenoid</b>						
	-	2-pin to VDMA 4-pin to Desina	Internal Internal	940 940	533013 540818	JMDH-5/2-D-2-M12-C JMDH-5/2-D-2-M12D-C
	With dominant signal at 14	2-pin to VDMA 4-pin to Desina	Internal Internal	940 940	539077 540817	JMDDH-5/2-D-2-M12-C JMDDH-5/2-D-2-M12D-C
<b>5/3-way valve</b>						
	Normally closed, mechanical spring reset method	2-pin to VDMA 4-pin to Desina	Internal Internal	1000 1000	539078 540815	MDH-5/3G-D-2-M12-C MDH-5/3G-D-2-M12D-C
	Normally exhausted, mechanical spring reset method	2-pin to VDMA 4-pin to Desina	Internal Internal	1000 1000	533016 540814	MDH-5/3E-D-2-M12-C MDH-5/3E-D-2-M12D-C
	Normally open, mechanical spring reset method	2-pin to VDMA 4-pin to Desina	Internal Internal	1000 1000	533006 540816	MDH-5/3B-D-2-M12-C MDH-5/3B-D-2-M12D-C

## Data sheet – Width 65 mm

-  - Flow rate  
Up to 4500 l/min

-  - Voltage  
24 V DC

**General technical data**

Design	Piston spool valve			
Sealing principle	Soft			
Actuation type	Electric			
Type of control	Piloted			
Flow direction	Non-reversible			
Exhaust air function	Can be throttled			
Manual override	Non-detenting			
Type of mounting	On sub-base, with through-hole and screw			
Mounting position	Any			
Nominal width	[mm]	14.5		
Overlap	Positive overlap			
Width	[mm]	65		
Grid dimension	[mm]	71		
Pneumatic connections	Sub-base, size 3 to ISO 5599-1			
Noise level	[dB (A)]	85		
Conforms to standard	ISO 5599-1			

**Flow rates**

Valve function	5/2-way valve	5/3-way valve		
		Normally closed	Normally exhausted	Normally open
Standard nominal flow rate	[l/min]	4500	4100	4600
				4000

**Switching times [ms]**

		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way valve, single solenoid	MDH-5/2...	54	57	–	–
	MDH-5/2...-FR...	28	68	–	–
5/2-way valve, double solenoid	JMDH-...	–	–	21	–
	JMDDH-...	–	–	23	23
5/3-way valve	MDH-5/3G-...	35	79	–	–
	MDH-5/3E-...	36	84	–	–
	MDH-5/3B-...	36	84	–	–


## Technical data – Width 65 mm

Operating and environmental conditions		
Reset method	Pneumatic spring	Mechanical spring
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[bar]	2 ... 10
Ambient temperature	[°C]	-10 ... +50
Temperature of medium	[°C]	-10 ... +50
Safety characteristics		
Max. positive test pulse with 0 signal	[μs]	3800
Max. negative test pulse on 1 signal	[μs]	4900
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27	
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6	
Electrical data		
Electrical connection	M12x1	
Characteristic coil data	Voltage Power	[V DC] [W]
Permissible voltage fluctuations	[%]	±10
Duty cycle	[%]	100
Degree of protection to EN 60529	IP65	
Materials		
Housing	Die-cast aluminium	
Seals	HNBR, NBR	
Note on materials	RoHS-compliant	

## Technical data – Width 65 mm

## Dimensions

5/2-way valves, single solenoid


Download CAD data → [www.festo.com](http://www.festo.com)

- [1] Solenoid coil can be repositioned by 90° regardless of the manual override
- [2] Manual override
- [3] Captive retaining screws
- [4] Slot for inscription label
- [5] LED display
- [6] Connection for power supply  
M12x1  
2-pin coil to VDMA  
4-pin coil to Desina

Type	B1	B2	B3	B4	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
MDH-5/2 ...	65	48	12	30	M8	104.2	94.2	55	12	62.5	165.9	145.4	72.7	64	32	-
MDH-5/2- ... -FR...											182.5	140.6				

5/2-way double solenoid valves, 5/3-way valves

- [1] Solenoid coil can be repositioned by 90° regardless of the manual override
- [2] Manual override
- [3] Captive retaining screws
- [4] Slot for inscription label
- [5] LED display
- [6] Connection for power supply  
M12x1  
2-pin coil to VDMA  
4-pin coil to Desina




Type	B1	B2	B3	B4	D1	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5	L6
JMDH-5/2- ...	65	48	12	30	M8	104.2	94.2	55	12	-	186.4	145.4	72.7	64	32	146.9
JMDDH-5/2- ...											145.4	72.7				
MDH-5/3...											184	92				

## Ordering data – Width 65 mm


### Pin allocation

M12 plug – 2-pin to VDMA



- 1 Unused
- 2 Unused
- 3 com (-)
- 4 Signal (+)

M12 plug – 4-pin to Desina



- 1 Connected to 2
- 2 Connected to 1
- 3 com (-)
- 4 Signal (+)

Ordering data	Description	Coil	Pilot air supply	Weight [g]	Part no.	Type
<b>5/2-way valve, single solenoid</b>						
	Pneumatic spring reset method	2-pin to VDMA 4-pin to Desina	Internal Internal	1000 1000	533009 540819	MDH-5/2-D-3-M12-C MDH-5/2-D-3-M12D-C
	Mechanical spring reset method	2-pin to VDMA 4-pin to Desina	Internal Internal	1000 1000	533012 540820	MDH-5/2-D-3-FR-M12-C MDH-5/2-D-3-FR-M12D-C
<b>5/2-way valve, double solenoid</b>						
	-	2-pin to VDMA 4-pin to Desina	Internal Internal	1100 1100	533015 540825	JMDH-5/2-D-3-M12-C JMDH-5/2-D-3-M12D-C
	With dominant signal at 14	2-pin to VDMA 4-pin to Desina	Internal Internal	1100 1100	539081 540824	JMDDH-5/2-D-3-M12-C JMDDH-5/2-D-3-M12D-C
<b>5/3-way valve</b>						
	Normally closed, mechanical spring reset method	2-pin to VDMA 4-pin to Desina	Internal Internal	1120 1120	539080 540822	MDH-5/3G-D-3-M12-C MDH-5/3G-D-3-M12D-C
	Normally exhausted, mechanical spring reset method	2-pin to VDMA 4-pin to Desina	Internal Internal	1120 1120	533017 540821	MDH-5/3E-D-3-M12-C MDH-5/3E-D-3-M12D-C
	Normally open, mechanical spring reset method	2-pin to VDMA 4-pin to Desina	Internal Internal	1120 1120	533007 540823	MDH-5/3B-D-3-M12-C MDH-5/3B-D-3-M12D-C

## Data sheet – Width 76 mm

-  - Flow rate  
Up to 6000 l/min

-  - Voltage  
24 V DC  
48 V AC

**General technical data**

Design	Piston spool valve	
Sealing principle	Soft	
Actuation type	Electric	
Type of control	Piloted	
Flow direction	Non-reversible	
Exhaust air function	Can be throttled	
Manual override	Non-detenting	
Type of mounting	On sub-base, with through-hole and screw	
Mounting position	Any	
Nominal width	[mm]	18
Overlap	Positive overlap	
Width	[mm]	76
Grid dimension	[mm]	82
Pneumatic connections	Sub-base, size 4 to ISO 5599-1	
Noise level	[dB (A)]	85
Conforms to standard	ISO 5599-1	

**Flow rates**

Valve function	5/2-way valve	5/3-way valve
Standard nominal flow rate	[l/min]	6000

**Switching times [ms]**

		Switching time on	Switching time off	Switching time changeover
5/2-way valve	Single solenoid	120	160	–
	Double solenoid	–	–	40
5/3-way valve		85	290	–

## Standards-based valves to ISO 5599-1, square plug, design A

### Technical data – Width 76 mm

Operating and environmental conditions			
Valve function	5/2-way valve, single solenoid	5/2-way valve, double solenoid	5/3-way valve
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]		
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)		
Operating pressure	[bar]	3 ... 16	2 ... 16
Ambient temperature	[°C]	-10 ... +50	3 ... 16
Temperature of medium	[°C]	-10 ... +60	

Safety characteristics			
Type	MDH-...-D-4-24DC, JMDH-...-D-4-24DC	MDH-...-D-4, JMDH-...-D-4	
Max. positive test pulse with 0 signal	[s]	4300	-
Max. negative test pulse on 1 signal	[s]	2100	-

Electrical data – MDH-...-24DC, JMDH-...-24DC			
	DC voltage	Alternating voltage	
Electrical connection	To DIN EN 175301-803		
Coil characteristics	Voltage	[V DC]	24
		[V AC]	-
	Frequency	[Hz]	48
	Power	[W]	50/60
	Pickup power	[VA]	6.8
	Holding power	[VA]	-
Duty cycle	[%]	14.5	-
Degree of protection to EN 60529		9.9	100
			IP65

Electrical data – Pilot valve MDH-3/2...			
Type	MDH-3/2-24DC	MDH-3/2-24DC/42AC	MDH-3/2-110AC
Electrical connection	Plug, square design to EN 175301-803, type A		
Coil characteristics	Voltage	[V DC]	24
		[V AC]	-
	Frequency	[Hz]	48
	Power	[W]	53
	Pickup power	[VA]	60
	Holding power	[VA]	-
Permissible voltage fluctuations	[%]	50	42
Permissible frequency fluctuations	[%]	60	42
Duty cycle	[%]	50	42
Degree of protection to EN 60529		60	42
		110	110
		-	230
			230
	Power	[W]	50
	Pickup power	[VA]	6.3
	Holding power	[VA]	-
Permissible voltage fluctuations	[%]	12	12
Permissible frequency fluctuations	[%]	14.5	14.5
Duty cycle	[%]	12	12
Degree of protection to EN 60529		14.5	12
		-	10.5
			7.6
	Power	[W]	-
	Pickup power	[VA]	10.5
	Holding power	[VA]	7.6
Permissible voltage fluctuations	[%]	7	7
Permissible frequency fluctuations	[%]	10.5	10.5
Duty cycle	[%]	10	10
Degree of protection to EN 60529		10	10
		-	10
			10


  

Materials	
Housing	Aluminium
Seals	NBR
Note on materials	RoHS-compliant

## Technical data – Width 76 mm

## Dimensions


5/2-way valves, single solenoid

Download CAD data → [www.festo.com](http://www.festo.com)

Type	B1	B2	D1	H1	H2	H3	H4	L1	L2	L3	L4	L5
MDH-5/2 ...	76	58	M8	139	110.5	74	14	182	67.5	80	40	81

5/2-way double solenoid valves, 5/3-way valves

- [1] Connection for plug socket with plug pattern to EN 175301-803, design A → page 130
- [2] Manual override
- [3] Captive retaining screws
- [4] Solenoid coil can be repositioned by 90° regardless of the manual override



Type	B1	B2	D1	H1	H2	H3	H4	L1	L2	L3	L4	L5
JMDH-5/2- ...	76	58	M8	139	110.5	74	14	182	135	80	40	162
MDH-5/3...												

## Standards-based valves to ISO 5599-1, square plug, design A

### Ordering data – Width 76 mm


Ordering data		Description	Voltage	Pilot air supply	Weight [g]	Part no.	Type
<b>5/2-way valve, single solenoid</b>							
	Pneumatic spring reset method	24 V DC	Internal	2600	12457	MDH-5/2-3/4-D-4-24DC	
		-	Internal	2600	14544	MDH-5/2-3/4-D-4 <sup>1)</sup>	
<b>5/2-way valve, double solenoid</b>							
	-	24 V DC	Internal	2600	12458	JMDH-5/2-3/4-D-4-24DC	
		-	Internal	2600	14545	JMDH-5/2-3/4-D-4 <sup>1)</sup>	
<b>5/3-way valve</b>							
	Normally closed, mechanical spring reset method	24 V DC	Internal	2600	12459	MDH-5/3G-3/4-D-4-24DC	
		-	Internal	2600	14546	MDH-5/3G-3/4-D-4 <sup>1)</sup>	
	Normally exhausted, mechanical spring reset method	24 V DC	Internal	2600	12460	MDH-5/3E-3/4-D-4-24DC	
		-	Internal	2600	14547	MDH-5/3E-3/4-D-4 <sup>1)</sup>	
<b>Usable pilot valves</b>							
	Electrical connection to EN 175301-803 design A	24 V DC	-	140	119600	MDH-3/2-24DC	
		24 V DC/ 42 V AC	-	140	119603	MDH-3/2-24DC/42AC	
		110 V AC	-	140	119601	MDH-3/2-110AC	
		110 V DC/ 230 V AC	-	140	119602	MDH-3/2-230AC	

1) Without pilot valve. The part number of the pilot valve must be added after the type code when ordering.

Order example: 14546 MDH-5/3G-3/4-D-4-119602 (for MDH-3/2-230AC with part no. 119602)

## Peripherals overview


### Valve on individual sub-base



Individual components		Type	Brief description	→ Page/Internet
[1]	Push-in fitting	QS-...	For connecting compressed air tubing with standard O.D.	qs
[2]	Sub-base	VABS-S1...	Pneumatic connections at the side	97
	Individual sub-base	NAS-...	Pneumatic connections at the side	97
		NAU-...	Pneumatic connections underneath	100
[3]	Silencers	U-...	For mounting in exhaust ports	silencer
[4]	Pneumatic valve	VL-...	Port pattern to ISO 5599-1	80
		J-...	Port pattern to ISO 5599-1	80
		JD-...	Port pattern to ISO 5599-1	80

## Peripherals overview


### Manifold assembly



Individual components		Type	Brief description	→ Page/Internet
[1]	End plates	VABE-S1...	For sealing the manifold sub-bases	109
[2]	Push-in fitting	QS...	For connecting compressed air tubing with standard O.D.	qs
[3]	Silencers	U...	For mounting in exhaust ports	silencer
[4]	Manifold sub-base	VABV-S1...	With ports 2 and 4	102
[5]	Duct separation	VABD-S1-1...	For sealing ducts 1, 3, 5, 12 and 14 between end plate and manifold sub-base, e.g. to create pressure zones	113
[6]	Supply plate	VABF-S1-1...	With ports for air supply 1 and exhausts 3 and 5	104
[7]	Pneumatic valve	VL...	Port pattern to ISO 5599-1	80
		J...	Port pattern to ISO 5599-1	80
		JD...	Port pattern to ISO 5599-1	80
[8]	Cover plate	NDV...	For sealing unused manifold sub-bases	112
[9]	Throttle plate	VABF-S1-...-F1B1-C	Controls the flow of exhaust air in ducts 3 and 5	116
		GRO-ZP...	Controls the flow of exhaust air in ducts 3 and 5	116
[10]	Regulator plate	VABF-S1-...-R...	Pressure regulator for manually setting a particular pressure in the regulated port upstream or downstream of the valve	123
		LR-ZP...	Pressure regulator for manually setting a particular pressure in the regulated port upstream or downstream of the valve	123

## Peripherals overview

### Manifold assembly



### Individual components

	Type	Brief description	→ Page/Internet
[1]	End plate kit	For sealing the manifold sub-bases	108
[2]	Push-in fitting	For connecting compressed air tubing with standard O.D.	qs
[3]	90° connection plate	For routing ports 2 and 4 to the front	107
[4]	Manifold sub-base	With ports 2 and 4 underneath	102
[5]	Isolating disc	For sealing ducts 1, 3, 5 between end plate and manifold sub-base, e.g. to create pressure zones	112
[6]	Intermediate plate	For connecting manifold sub-bases of different sizes	114
[7]	Manifold sub-base with 90° connections	With ports 2 and 4 either underneath or to the front	107
[8]	Silencers	For mounting in exhaust ports	silencer
[9]	Pneumatic valve	Port pattern to ISO 5599-1	80
	J-...	Port pattern to ISO 5599-1	80
	JD-...	Port pattern to ISO 5599-1	80
[10]	Cover plate	For sealing unused manifold sub-bases	112
[11]	Throttle plate	Controls the flow of exhaust air in ducts 3 and 5	116
	GRO-ZP-...	Controls the flow of exhaust air in ducts 3 and 5	116
[12]	Regulator plate	Pressure regulator for manually setting a particular pressure in the regulated port upstream or downstream of the valve	123
	LR-ZP-...	Pressure regulator for manually setting a particular pressure in the regulated port upstream or downstream of the valve	123

## Technical data – Width 42 mm

-  Flow rate  
1200 l/min



General technical data		
Type	VL- ... -C, J ... -C	VL- ... -EX, J ... -EX
Design	Piston spool valve	Piston spool valve
Sealing principle	Soft	Soft
Actuation type	Pneumatic	Pneumatic
Type of control	Direct	Direct
Flow direction	Reversible	Reversible
	VL-5/2-D-1-C: non-reversible	VL-5/2-D-1-C-EX: non-reversible
Exhaust air function	Can be throttled	Can be throttled
Manual override	None	None
Type of mounting	On sub-base via through-hole	On sub-base via through-hole
Mounting position	Any	Any
Nominal width	[mm]	8
Overlap		Positive overlap
Width	[mm]	42
Grid dimension	[mm]	43
Pneumatic connections		Sub-base, size 1 to ISO 5599-1
Noise level	[dB (A)]	85
Conforms to standard		ISO 5599-1
Certification	UL - Recognized (OL)	-
Maritime classification <sup>1)</sup>	See certificate	-

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

Flow rates					
Standard nominal flow rate		[l/min]	1200		
Switching times [ms]			Switching time on	Switching time off	Switching time changeover
5/2-way valve, monostable	VL-5/2-D-1-C	9	18	-	-
	VL-5/2-D-1-C-EX	9	18	-	-
	VL-5/2-D-1-FR-C	6	23	-	-
	VL-5/2-D-1-FR-C-EX	6	23	-	-
5/2-way valve, bistable	J-5/2-D-1-C	-	-	6	-
	J-5/2-D-1-C-EX	-	-	6	-
	JD-5/2-D-1-C	-	-	6	4
	JD-5/2-D-1-C-EX	-	-	6	4
5/3-way valve	VL-5/3G-D-1-C	7	44	-	-
	VL-5/3G-D-1-C-EX	7	44	-	-
	VL-5/3E-D-1-C	7	45	-	-
	VL-5/3E-D-1-C-EX	7	45	-	-
	VL-5/3B-D-1-C	7	44	-	-
	VL-5/3B-D-1-C-EX	7	44	-	-

## Technical data – Width 42 mm

<b>ATEX</b>	
Type	VL- ... -EX, J ... -EX
ATEX category for gas	II 2G
Type of ignition protection for gas	Ex h IIC T4 Gb
ATEX category for dust	II 2D
Type of ignition protection for dust	Ex h IIIC T130°C Db
Explosion-proof ambient temperature	[°C]
CE marking (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)

<b>Operating and environmental conditions</b>	
Valve function	5/2-way valve
	Monostable
	Bistable
Pneumatic spring	Mechanical spring
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[bar]
2 ... 16	-0.9 ... +16
2 ... 16	-0.9 ... +16
Pilot pressure	[bar]
2 ... 16	3 ... 16
Ambient temperature	[°C]
-10 ... +60	2 ... 16
Temperature of medium	[°C]
-10 ... +60	3 ... 16

<b>Safety characteristics</b>	
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6


<b>Materials</b>	
Housing	Die-cast aluminium
Seals	HNBR, NBR
Note on materials	RoHS-compliant

## Technical data – Width 42 mm

### Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)


5/2-way valves, pneumatic spring reset method, 5/2-way bistable valves



- [3] Captive retaining screws
- [4] Slot for inscription label

Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/2- ...	42	28	6	M5	38	9	46.5	87.6	43.8	36	18
J-5/2- ...											
JD-5/2- ...											

5/2-way valves, mechanical spring reset method




- [3] Captive retaining screws
- [4] Slot for inscription label

Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/2- ...-FR- ...	42	28	6	M5	38	9	46.5	98	43.8	36	18

## Technical data – Width 42 mm


## Dimensions

5/3-way valves

Download CAD data → [www.festo.com](http://www.festo.com)






[3] Captive retaining screws

[4] Slot for inscription label



Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/3...	42	28	6	M5	38	9	46.5	108.4	54.2	36	18

## Technical data – Width 42 mm

Ordering data	Description	Weight [g]	Part no.	Type
<b>5/2-way valve, monostable</b>				
	Pneumatic spring reset method	-	290	151009 VL-5/2-D-1-C
		ATEX category → page 81	290	536007 VL-5/2-D-1-C-EX
	Mechanical spring reset method	-	290	151014 VL-5/2-D-1-FR-C
		ATEX category → page 81	290	536010 VL-5/2-D-1-FR-C-EX
<b>5/2-way valve, bistable</b>				
	-	-	290	151007 J-5/2-D-1-C
		ATEX category → page 81	290	536013 J-5/2-D-1-C-EX
	With dominant signal at 14	-	290	151008 JD-5/2-D-1-C
		ATEX category → page 81	290	536016 JD-5/2-D-1-C-EX
<b>5/3-way valve</b>				
	Normally closed Mechanical spring reset method	-	320	151010 VL-5/3G-D-1-C
		ATEX category → page 81	320	536019 VL-5/3G-D-1-C-EX
	Normally exhausted Mechanical spring reset method	-	320	151011 VL-5/3E-D-1-C
		ATEX category → page 81	320	536022 VL-5/3E-D-1-C-EX
	Normally pressurised Mechanical spring reset method	-	320	151012 VL-5/3B-D-1-C
		ATEX category → page 81	320	536025 VL-5/3B-D-1-C-EX

## Technical data – Width 52 mm

-  - Flow rate  
2300 l/min



General technical data		
Type	VL- ... -C, J ... -C	VL- ... -EX, J ... -EX
Design	Piston spool valve	Piston spool valve
Sealing principle	Soft	Soft
Actuation type	Pneumatic	Pneumatic
Type of control	Direct	Direct
Flow direction	Reversible	Reversible
	VL-5/2-D-2-C: non-reversible	VL-5/2-D-2-C-EX: non-reversible
Exhaust air function	Can be throttled	Can be throttled
Manual override	None	None
Type of mounting	On sub-base, with through-hole and screw	On sub-base, with through-hole and screw
Mounting position	Any	Any
Nominal width	[mm]	11.5
Overlap		Positive overlap
Width	[mm]	52
Grid dimension	[mm]	56
Pneumatic connections		Sub-base, size 2 to ISO 5599-1
Noise level	[dB (A)]	85
Conforms to standard		ISO 5599-1
Certification	UL - Recognized (OL)	-
Maritime classification <sup>1)</sup>	See certificate	-

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

Flow rates					
Standard nominal flow rate		[l/min]			
<b>Switching times [ms]</b>					
		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way valve, monostable	VL-5/2-D-2-C	23	39	-	-
	VL-5/2-D-2-C-EX	23	39	-	-
	VL-5/2-D-2-FR-C	11	39	-	-
	VL-5/2-D-2-FR-C-EX	11	39	-	-
5/2-way valve, bistable	J-5/2-D-2-C	-	-	8	-
	J-5/2-D-2-C-EX	-	-	8	-
	JD-5/2-D-2-C	-	-	8	8
	JD-5/2-D-2-C-EX	-	-	8	8
5/3-way valve	VL-5/3G-D-2-C	15	56	-	-
	VL-5/3G-D-2-C-EX	15	56	-	-
	VL-5/3E-D-2-C	16	59	-	-
	VL-5/3E-D-2-C-EX	16	59	-	-
	VL-5/3B-D-2-C	15	57	-	-
	VL-5/3B-D-2-C-EX	15	57	-	-

## Standards-based valves to ISO 5599-1, pneumatic valves

### Technical data – Width 52 mm

ATEX	
Type	VL- ... -EX, J ... -EX
ATEX category for gas	II 2G
Type of ignition protection for gas	Ex h IIC T4 Gb
ATEX category for dust	II 2D
Type of ignition protection for dust	Ex h IIIC T130°C Db
Explosion-proof ambient temperature	[°C]
CE marking (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)

Operating and environmental conditions	
Valve function	5/2-way valve
	Monostable
	Bistable
Pneumatic spring	Mechanical spring
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[bar]
2 ... 16	-0.9 ... +16
Pilot pressure	[bar]
2 ... 16	3 ... 16
Ambient temperature	[°C]
-10 ... +60	2 ... 16
Temperature of medium	[°C]
-10 ... +60	3 ... 16

Safety characteristics	
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6


Materials	
Housing	Die-cast aluminium
Seals	HNBR, NBR
Note on materials	RoHS-compliant

## Technical data – Width 52 mm

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

5/2-way valves, pneumatic spring reset method, 5/2-way bistable valves




- [3] Captive retaining screws
- [4] Slot for inscription label

Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/2- ...	54	38	9	M6	48	9.5	56.5	123.4	61.7	48	24
J-5/2- ...											
JD-5/2- ...											

5/2-way valves, mechanical spring reset method

- [3] Captive retaining screws
- [4] Slot for inscription label




Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/2- ... -FR- ...	54	38	9	M6	48	9.5	56.5	140.7	61.7	48	24

## Technical data – Width 52 mm

### Dimensions

5/3-way valves








Download CAD data → [www.festo.com](http://www.festo.com)



- [3] Captive retaining screws
- [4] Slot for inscription label

Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/3...	54	38	9	M6	48	9.5	56.5	158	79	48	24

## Technical data – Width 52 mm

Ordering data	Description	Weight [g]	Part no.	Type
<b>5/2-way valve, monostable</b>				
	Pneumatic spring reset method  Mechanical spring reset method	–	550	<b>151845</b> VL-5/2-D-2-C
		ATEX category → page 86	550	<b>536008</b> VL-5/2-D-2-C-EX
	Mechanical spring reset method	–	550	<b>151844</b> VL-5/2-D-2-FR-C
		ATEX category → page 86	550	<b>536011</b> VL-5/2-D-2-FR-C-EX
<b>5/2-way valve, bistable</b>				
	–	–	550	<b>151846</b> J-5/2-D-2-C
		ATEX category → page 86	550	<b>536014</b> J-5/2-D-2-C-EX
	With dominant signal at 14	–	550	<b>151847</b> JD-5/2-D-2-C
		ATEX category → page 86	550	<b>536017</b> JD-5/2-D-2-C-EX
<b>5/3-way valve</b>				
	Normally closed Mechanical spring reset method	–	825	<b>151848</b> VL-5/3G-D-2-C
		ATEX category → page 86	825	<b>536020</b> VL-5/3G-D-2-C-EX
	Normally exhausted Mechanical spring reset method	–	825	<b>151849</b> VL-5/3E-D-2-C
		ATEX category → page 86	825	<b>536023</b> VL-5/3E-D-2-C-EX
	Normally pressurised Mechanical spring reset method	–	825	<b>151850</b> VL-5/3B-D-2-C
		ATEX category → page 86	825	<b>536026</b> VL-5/3B-D-2-C-EX

## Technical data – Width 65 mm

-  Flow rate  
Up to 4600 l/min



General technical data		
Type	VL- ... -C, J ... -C	VL- ... -EX, J ... -EX
Design	Piston spool valve	Piston spool valve
Sealing principle	Soft	Soft
Actuation type	Pneumatic	Pneumatic
Type of control	Direct	Direct
Flow direction	Reversible	Reversible
	VL-5/2-D-3-C: non-reversible	VL-5/2-D-3-C-EX: non-reversible
Exhaust air function	Can be throttled	Can be throttled
Manual override	None	None
Type of mounting	On sub-base, with through-hole and screw	On sub-base, with through-hole and screw
Mounting position	Any	Any
Nominal width	[mm]	14.5
Overlap		Positive overlap
Width	[mm]	65
Grid dimension	[mm]	71
Pneumatic connections		Sub-base, size 3 to ISO 5599-1
Noise level	[dB (A)]	85
Conforms to standard		ISO 5599-1
Certification		UL - Recognized (OL)
Maritime classification <sup>1)</sup>		See certificate

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

Flow rates		5/2-way valve	5/3-way valve		
Valve function			Normally closed	Normally exhausted	Normally open
Standard nominal flow rate	[l/min]	4500	4100	4600	4100

## Technical data – Width 65 mm

Switching times [ms]		Switching time on	Switching time off	Switching time changeover	Switching time changeover (dominant)
5/2-way valve, monostable	VL-5/2-D-1-C	29	36	–	–
	VL-5/2-D-1-C-EX	29	36	–	–
	VL-5/2-D-1-FR-C	13	43	–	–
	VL-5/2-D-1-FR-C-EX	13	43	–	–
5/2-way valve, bistable	J-5/2-D-1-C	–	–	8	–
	J-5/2-D-1-C-EX	–	–	8	–
	JD-5/2-D-1-C	–	–	8	8
	JD-5/2-D-1-C-EX	–	–	8	8
5/3-way valve	VL-5/3G-D-1-C	17	61	–	–
	VL-5/3G-D-1-C-EX	17	61	–	–
	VL-5/3E-D-1-C	18	63	–	–
	VL-5/3E-D-1-C-EX	18	63	–	–
	VL-5/3B-D-1-C	16	60	–	–
	VL-5/3B-D-1-C-EX	16	60	–	–

ATEX	
Type	VL- ... -EX, J ... -EX
ATEX category for gas	II 2G
Type of ignition protection for gas	Ex h IIC T4 Gb
ATEX category for dust	II 2D
Type of ignition protection for dust	Ex h IIIC T130°C Db
Explosion-proof ambient temperature	[°C]
CE marking (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)

Operating and environmental conditions	
Valve function	5/2-way valve
	Monostable
	Pneumatic spring
	Mechanical spring
5/2-way valve	5/3-way valve
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[bar]
2 ... 16	-0.9 ... +16
Pilot pressure	[bar]
2 ... 16	3 ... 16
Ambient temperature	[°C]
-10 ... +60	2 ... 16
Temperature of medium	[°C]
-10 ... +60	3 ... 16

Safety characteristics	
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6


Materials	
Housing	Die-cast aluminium
Seals	HNBR, NBR
Note on materials	RoHS-compliant

## Technical data – Width 65 mm

### Dimensions

5/2-way valves, pneumatic spring reset method, 5/2-way bistable valves

Download CAD data → [www.festo.com](http://www.festo.com)




- [3] Captive retaining screws
- [4] Slot for inscription label

Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/2-...	65	48	12	M8	55	12	63.5	145.4	72.7	64	32
J-5/2-...											
JD-5/2-...											

5/2-way valves, mechanical spring reset method

- [3] Captive retaining screws
- [4] Slot for inscription label




Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/2-...-FR...	65	48	12	M8	55	12	63.5	164.7	72.7	64	32

## Technical data – Width 65 mm

## Dimensions

5/3-way valves

Download CAD data → [www.festo.com](http://www.festo.com)

Type	B1	B2	B3	D1	H3	H4	H5	L2	L3	L4	L5
VL-5/3...	65	48	12	M8	55	12	63.5	184	92	64	32

## Ordering data

Circuit symbol	Description	Weight [g]	Part no.	Type
<b>5/2-way valve, monostable</b>				
	Pneumatic spring reset method	-	810	151864 VL-5/2-D-3-C
	ATEX category → page 91	810	536009	VL-5/2-D-3-C-EX
	Mechanical spring reset method	-	810	151863 VL-5/2-D-3-FR-C
	ATEX category → page 91	810	536012	VL-5/2-D-3-FR-C-EX
<b>5/2-way valve, bistable</b>				
	-	810	151865	J-5/2-D-3-C
	ATEX category → page 91	810	536015	J-5/2-D-3-C-EX
	With dominant signal at 14	-	810	151866 JD-5/2-D-3-C
	ATEX category → page 91	810	536018	JD-5/2-D-3-C-EX
<b>5/3-way valve</b>				
	Normally closed Mechanical spring reset method	-	910	151867 VL-5/3G-D-3-C
	ATEX category → page 91	910	536021	VL-5/3G-D-3-C-EX
	Normally exhausted Mechanical spring reset method	-	910	151868 VL-5/3E-D-3-C
	ATEX category → page 91	910	536024	VL-5/3E-D-3-C-EX
	Normally pressurised Mechanical spring reset method	-	910	151869 VL-5/3B-D-3-C
	ATEX category → page 91	910	536027	VL-5/3B-D-3-C-EX

## Technical data – Width 76 mm

-  - Flow rate  
Up to 6000 l/min

**General technical data**

Design	Piston spool valve	
Sealing principle	Soft	
Actuation type	Pneumatic	
Type of control	Direct	
Flow direction	Reversible	
Exhaust air function	Can be throttled	
Manual override	None	
Type of mounting	On sub-base, with through-hole and screw	
Mounting position	Any	
Nominal width	[mm]	18
Overlap	Positive overlap	
Width	[mm]	76
Grid dimension	[mm]	82
Pneumatic connections	Sub-base, size 4 to ISO 5599-1	
Noise level	[dB (A)]	85
Conforms to standard	ISO 5599-1	

**Flow rates**

Valve function	5/2-way valve	5/3-way valve	
Standard nominal flow rate	[l/min]	6000	4800

**Switching times [ms]**

		Switching time on	Switching time off	Switching time changeover
5/2-way valve, monostable	VL-5/2-3/4-D-4	25	90	–
5/2-way valve, bistable	J-5/2-3/4-D-4	–	–	20
5/3-way valve	VL-5/3G-3/4-D-4	40	130	–
	VL-5/3E-3/4-D-4	50	170	–

## Technical data – Width 76 mm

Operating and environmental conditions		5/2-way valve		5/3-way valve	
Valve function		Monostable	Bistable		
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]				
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]				
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)				
Operating pressure	[bar]	-0.9 ... +16	-0.9 ... +16	-0.9 ... +16	
Pilot pressure	[bar]	3 ... 16	2 ... 16	3 ... 16	
Ambient temperature	[°C]	-10 ... +60			
Temperature of medium	[°C]	-10 ... +60			


  

Materials	
Housing	Aluminium
Seals	NBR
Note on materials	RoHS-compliant

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)





5/3-way valves



The technical drawings illustrate the physical dimensions of the valve. The top drawing shows the front view with dimensions L2, L3, and L4. The bottom drawing shows the side view with dimensions D1, B1, B2, H3, H4, L2, L3, L4, and L5. Callout [3] points to the captive retaining screws.

Type	B1	B2	D1	H3	H4	L2	L3	L4	L5
VL-5/2-3/4-D-4	76	58	M8	74	14	182	91	80	40
J-5/2-3/4-D-4									
VL-5/3E-3/4-D-4									
VL-5/3G-3/4-D-4									

Technical data – Width 76 mm


Ordering data	Description	Weight [g]	Part no.	Type
<b>5/2-way valve, monostable</b>				
	Mechanical spring reset method	1800	12461	VL-5/2-3/4-D-4
<b>5/2-way valve, bistable</b>				
	-	1800	12462	J-5/2-3/4-D-4
<b>5/3-way valve</b>				
	Normally closed Mechanical spring reset method	2000	12463	VL-5/3G-3/4-D-4
	Normally exhausted Mechanical spring reset method	2000	12464	VL-5/3E-3/4-D-4

## Accessories

**Individual sub-base NAS**  
Sub-base VABS

Connections at side

Materials:

Die-cast aluminium  
Anodised aluminium

<b>General technical data</b>					
Type	NAS-1/4	NAS-3/8	NAS-1/2	NAS-3/4	VABS
Conforms to standard	ISO 5599-1				–
Based on standard	–				ISO 5599-1
Actuation type	–				Electric
Sealing principle	–				Soft
Mounting position	–				Any
Suitable for vacuum	–				Yes
Type of mounting	With through-hole			Via through-hole for M5 screw	
<b>Materials</b>					
Type	NAS-1/4	NAS-3/8	NAS-1/2	NAS-3/4	VABS
Sub-base	Die-cast aluminium		Anodised aluminium	Die-cast aluminium	
Note on materials	–	–	–	RoHS-compliant	
	Free of copper and PTFE			–	–

<b>Operating and environmental conditions</b>					
Type	NAS-1/4	NAS-3/8	NAS-1/2	NAS-3/4	VABS
Operating medium	–		–	–	Compressed air to ISO 8573-1:2010 [7:4:4]
Pilot medium	–		–	–	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/pilot medium	–		–	–	Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure [bar]	–		–	–	0 ... 16
Pilot pressure [bar]	–		–	–	0 ... 10
Ambient temperature [°C]	–		–	–	-10 ... +60
Temperature of medium [°C]	–		–	–	-10 ... +60
Storage temperature [°C]	–		–	–	-20 ... +60
Corrosion resistance CRC <sup>1)</sup>	–		–	–	0
CE marking (see declaration of conformity) <sup>2)</sup>	–		–	–	To EU Low-Voltage Directive
Certification	c UL - Recognized (OL)			–	–

1) Corrosion resistance class CRC 0 to Festo standard FN 940070


No corrosion stress. Applies to small, visually unimportant standard parts such as threaded pins, circlips and clamping sleeves which are usually only available on the market in a phosphated or burnished version (and possibly oiled) as well as to ball bearings (for components < CRC 3) and plain bearings.

2) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

## Accessories

### Dimensions – Individual sub-base NAS


Download CAD data → [www.festo.com](http://www.festo.com)



Type	B1	D1	D2	D3	H1	H2	H4	H5	H6	L1	L2	L3	L4	L5
NAS-1/4-1A-ISO	48	G1/4	G1/8	5.5	32	10	9	20.3	20.3	110	98	23	60	46
NAS-3/8-2A-ISO	57	G3/8	G1/8	6.6	40	13	9	25	25	124	112	27	71	54
NAS-1/2-3A-ISO	71	G1/2	G1/8	6.6	32	18	9	16	16	149	136	32	91	64
NAS-3/4-4A-ISO	85	G3/4	G1/8	9	42	19	9	21	21	186	170	42	111	84

### Dimensions – Sub-base VABS

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B1	B2	B3	D1	D2	H1	H2	H3	H4	H5	H6
VABS-S1-1S-G38	48	46	23	G3/8	G1/8	38.5	5	16.3	13.5	26.5	13.5
VABS-S1-1S-N38				3/8 NPT	1/8 NPT						
VABS-S1-2S-G12	58	56	28	G1/2	G1/8	45	10	18	16	29	16
VABS-S1-2S-N12				1/2 NPT	1/8 NPT						

Type	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10
VABS-S1-1S-G38	110	98	6	57	26.5	42	26	45.4	32.3	22.7
VABS-S1-1S-N38										
VABS-S1-2S-G12	124	112	6	72	26	46	32	55	34.5	27.5
VABS-S1-2S-N12										

## Accessories

Ordering data		Width	Pneumatic connection		Weight [g]	Part no.	Type
Designation to VDMA			1, 2, 3, 4, 5	12, 14			
VDMA 24345-A-1	–	48 mm	G1/4	G1/8	190	★ 9484	NAS-1/4-1A-ISO
–	–		G3/8	–	230	8032642	VABS-S1-1S-G38
–	–		3/8 NPT	–	230	8032643	VABS-S1-1S-N38
VDMA 24345-A-2	–	58 mm	G3/8	G1/8	300	11310	NAS-3/8-2A-ISO
–	–		G1/2	–	380	8032644	VABS-S1-2S-G12
–	–		1/2 NPT	–	380	8032645	VABS-S1-2S-N12
VDMA 24345-A-3	–	–	G1/2	G1/8	360	10336	NAS-1/2-3A-ISO
VDMA 24345-A-4	–		G3/4	G1/8	1260	152813	NAS-3/4-4A-ISO

• Note: This product conforms to ISO 1179-1 and ISO 228-1.



## Accessories

### Individual sub-base NAU

Connections underneath

#### Materials:

Die-cast aluminium  
Anodised aluminium



#### General technical data

Conforms to standard	ISO 5599-1		
Type of mounting	With through-hole		

#### Materials


Type	NAU-1/4	NAU-3/8	NAU-1/2	NAU-3/4
Sub-base	Die-cast aluminium		Anodised aluminium	
Note on materials	Free of copper and PTFE		-	

#### Operating and environmental conditions

Type	NAU-1/4	NAU-3/8	NAU-1/2	NAU-3/4
Certification	c UL - Recognized (OL)	-	-	-

#### Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B1	D1	D2	D3	H1	H2	H3	H4	H5	L1	L2	L3	L4	L5
NAU-1/4-1B-ISO	46	G1/4	G1/8	5.5	30	10	5	7.5	20	110	98	23	60.7	46
NAU-3/8-2B-ISO	56	G3/8	G1/8	6.6	35	13	6.5	8.3	24	124	112	27	70	54
NAU-1/2-3B-ISO	71	G1/2	G1/8	6.6	32	18	9	10	30	149	136	33	90	66
NAU-3/4-4B-ISO	85	G3/4	G1/8	9	28	19	9.5	12	37	186	170	42	111	84

## Accessories

Ordering data		Pneumatic connection		Weight [g]	Part no.	Type
Designation to VDMA		1, 2, 3, 4, 5	12, 14			
VDMA 24345-B-1	G1/4	G1/8	–	★ 9485	NAU-1/4-1B-ISO	
VDMA 24345-B-2	G3/8	G1/8	450	11416	NAU-3/8-2B-ISO	
VDMA 24345-B-3	G1/2	G1/8	660	10337	NAU-1/2-3B-ISO	
VDMA 24345-B-4	G3/4	G1/8	1080	152814	NAU-3/4-4B-ISO	

Note: This product conforms to ISO 1179-1 and ISO 228-1.



## Accessories

<b>Manifold sub-base</b>	Connections underneath	
<b>NAV</b>	Materials:	
<b>VABV</b>	Die-cast aluminium Anodised aluminium	

Dimensions NAV → page115

General technical data					
Type	NAV-1/4	NAV-3/8	NAV-1/2	NAV-3/4	VABV
Conforms to standard	ISO 5599-1				–
Based on standard	–				ISO 5599-1
Maximum number of valve positions	–				1
Suitable for vacuum	–				Yes
Exhaust air function	–				Via throttle plate

Materials					
Type	NAV-1/4	NAV-3/8	NAV-1/2	NAV-3/4	VABV
Sub-base	Die-cast aluminium		Anodised aluminium		Die-cast aluminium
Note on materials	–		–		RoHS-compliant


Operating and environmental conditions					
Type	NAV-1/4	NAV-3/8	NAV-1/2	NAV-3/4	VABV
Operating medium	–	–	–	–	Compressed air to ISO 8573-1:2010 [7:4:4]
Pilot medium	–	–	–	–	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/pilot medium	–	–	–	–	Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[bar]	–	–	–	0 ... 10
Ambient temperature	[°C]	–	–	–	-10 ... +50
Temperature of medium	[°C]	–	–	–	-10 ... +50
Storage temperature	[°C]	–	–	–	-20 ... +60
Corrosion resistance CRC <sup>1)</sup>	–	–	–	–	0
CE marking (see declaration of conformity) <sup>2)</sup>	–	–	–	–	To EU Low-Voltage Directive
Certification	–	c UL - Recognized (OL)	–	–	–

1) Corrosion resistance class CRC 0 to Festo standard FN 940070  
No corrosion stress. Applies to small, visually unimportant standard parts such as threaded pins, circlips and clamping sleeves which are usually only available on the market in a phosphated or burnished version (and possibly oiled) as well as to ball bearings (for components < CRC 3) and plain bearings.

2) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

## Accessories

## Dimensions – VABV

Download CAD data → [www.festo.com](http://www.festo.com)

Type	B1	B2	B3	H1	H2	H3	H4	H5	L1	L2	L3
VABV-S1-1SB-G38	44	16.5	16	65	13.5	20.5	34	15	124	96.2	19.9
VABV-S1-1SB-N38											
VABV-S1-2SB-G12	59	19.5	22					35.5	14.5		
VABV-S1-2SB-N12											

Designation to VDMA	Width	Pneumatic connection		Weight [g]	Part no.	Type
		2, 4	12, 14			
VDMA 24345-C-1	–	G1/4	G1/8	240	★ 10173	NAV-1/4-1C-ISO
–	44 mm	G3/8	–	490	8029812	VABV-S1-1SB-G38
–		3/8 NPT	–	490	8029813	VABV-S1-1SB-N38
VDMA 24345-C-2	–	G3/8	G1/8	400	11305	NAV-3/8-2C-ISO
–	59 mm	G1/2	–	670	8029814	VABV-S1-2SB-G12
–		1/2 NPT	–	670	8029815	VABV-S1-2SB-N12
VDMA 24345-C-3	–	G1/2	G1/8	700	10175	NAV-1/2-3C-ISO
VDMA 24345-C-4	–	G3/4	G1/8	1400	11139	NAV-3/4-4C-ISO

Festo core product range



Generally ready for dispatch from the factory within 24 hours




Generally ready for dispatch from the factory within 5 days

## Accessories

### Supply plate VABF

Materials:

Die-cast aluminium  
Wrought aluminium alloy  
PA



#### General technical data

Based on standard	ISO 5599-1
Maximum number of valve positions	1
Suitable for vacuum	Yes
Exhaust air function	Via throttle plate

#### Materials

Type	VABF-S1-1-P1A11	VABF-S1-1-P1A12
Exhaust plate	Wrought aluminium alloy	PA
Supply plate	Anodised aluminium	Die-cast aluminium
Note on materials	RoHS-compliant	RoHS-compliant

#### Operating and environmental conditions

Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]	
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[bar]	0 ... 10
Ambient temperature	[°C]	-10 ... +50
Temperature of medium	[°C]	-10 ... +50
Storage temperature	[°C]	-20 ... +60
Corrosion resistance CRC <sup>1)</sup>	0	
CE marking (see declaration of conformity) <sup>2)</sup>	To EU Low-Voltage Directive	

1) Corrosion resistance class CRC 0 to Festo standard FN 940070

No corrosion stress. Applies to small, visually unimportant standard parts such as threaded pins, circlips and clamping sleeves which are usually only available on the market in a phosphated or burnished version (and possibly oiled) as well as to ball bearings (for components < CRC 3) and plain bearings.


2) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

## Accessories

## Dimensions


Download CAD data → [www.festo.com](http://www.festo.com)

Port 3 and 5 separated





Type	B1	B2	B3	H1	H3	H4	H5	L1	L2	L3	L4	L5
VABF-S1-1-P1A11	44	5.5	22	87	52.5	20.5	13.5	124	96.2	19.9	44	40

Port 3 and 5 combined



Type	B1	B2	B3	H1	H2	H3	H4	H5	L1	L2	L3
VABF-S1-1-P1A12	44	5.8	22	115.2	93.8	52.5	20.5	13.5	124	96.2	19.9

## Accessories

Ordering data		Width	Description	Pneumatic connection	Weight [g]	Part no.	Type
				1, 3, 5			
44 mm		Port 3 and 5 separated	G1/2	660	<b>8037655</b>	VABF-S1-1-P1A11-G12	
			1/2 NPT	660	<b>8037656</b>	VABF-S1-1-P1A11-N12	
		Port 3 and 5 combined	G1/2	650	<b>8037653</b>	VABF-S1-1-P1A12-G12	
			1/2 NPT	650	<b>8037654</b>	VABF-S1-1-P1A12-N12	

## Accessories

### 90°-connection plate NAW

Ports at side and top

#### Materials:

Die-cast aluminium  
Anodised aluminium

Dimensions → page 115



#### General technical data

Conforms to standard	ISO 5599-1			
----------------------	------------	--	--	--

#### Operating and environmental conditions

Type	NAW-1/4	NAW-3/8	NAW-1/2	NAW-3/4
Note on materials	Free of copper and PTFE			

#### Ordering data

Designation to VDMA	Pneumatic connection	Weight [g]	Part no.	Type
	2, 4	12, 14		
VDMA 24345-E-1	G1/4	G1/8	360	11304 NAW-1/4-1E-ISO
VDMA 24345-E-2	G3/8	G1/8	600	11307 NAW-3/8-2E-ISO
VDMA 24345-E-3	G1/2	G1/8	920	11309 NAW-1/2-3E-ISO
VDMA 24345-E-4	G3/4	G1/8	1550	11141 NAW-3/4-4E-ISO

### Manifold sub-base with 90° connections NAVW

Connections at the side and underneath

#### Materials:

Die-cast aluminium

Dimensions → page 115



#### General technical data

Conforms to standard	ISO 5599-1			
----------------------	------------	--	--	--

#### Operating and environmental conditions

Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]			
------------------	---	--	--	--

#### Ordering data

Pneumatic connection	Weight [g]	Part no.	Type
1, 2, 4	12, 14		
G1/4	G1/8	320	152789 NAVW-1/4-1-ISO
G3/8	G1/8	550	152790 NAVW-3/8-2-ISO
G1/2	G1/8	1020	152791 NAVW-1/2-3-ISO

▪ Note: This product conforms to ISO 1179-1 and ISO 228-1.

## Accessories

### End plate kit NEV

Materials:

Die-cast aluminium  
Anodised aluminium

Dimensions NEV → page 115



#### General technical data

Conforms to standard	ISO 5599-1		
----------------------	------------	--	--

#### Operating and environmental conditions

Type	NEV-1DA	NEV-2DA	NEV-3DA	NEV-4DA
Note on materials	Free of copper and PTFE		–	

#### Ordering data

Designation to VDMA	Pneumatic connection	Weight [g]	Part no.	Type
	1, 3, 5			
VDMA 24345-D-1	G3/8	280	★ 10174	NEV-1DA/DB-ISO
VDMA 24345-D-2	G1/2	450	11306	NEV-2DA/DB-ISO
VDMA 24345-D-3	G1	760	10176	NEV-3DA/DB-ISO
VDMA 24345-D-4	G1	1390	11140	NEV-4DA/DB-ISO


• Note: This product conforms to ISO 1179-1 and ISO 228-1.



## Accessories

### End plate VABE

Materials:  
Die-cast aluminium



#### General technical data

Based on standard	ISO 5599-1
Suitable for vacuum	Yes
Exhaust air function	Via throttle plate
Type of mounting	Via through-hole for M6 screw

#### Materials

End plate	Die-cast aluminium
Note on materials	RoHS-compliant

#### Operating and environmental conditions

Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[bar]
Ambient temperature	[°C]
Temperature of medium	[°C]
Storage temperature	[°C]
Corrosion resistance CRC <sup>1)</sup>	0
CE marking (see declaration of conformity) <sup>2)</sup>	To EU Low-Voltage Directive

1) Corrosion resistance class CRC 0 to Festo standard FN 940070

No corrosion stress. Applies to small, visually unimportant standard parts such as threaded pins, circlips and clamping sleeves which are usually only available on the market in a phosphated or burnished version (and possibly oiled) as well as to ball bearings (for components < CRC 3) and plain bearings.


2) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

## Accessories

### Dimensions


Left end plate

Download CAD data → [www.festo.com](http://www.festo.com)



Type	B1	B2	B3	B4	D1	D2	D3	H1	H2	H3	H4	L1	L2	L3	L4	L5	L6	L7	L8
VABE-S1-1L...G12	44	5.8	6	6	G1/2	G1/4	6.5	77.9	33	25.9	20	124.9	108	72	26.4	35.4	54	27	8.4
VABE-S1-1L...N12					1/2 NPT	1/4 NPT													
VABE-S1-2L...G34					G3/4	G1/4													
VABE-S1-2L...N34					3/4 NPT	1/4 NPT													

Right end plate



Type	B1	B3	B4	D1	D2	D3	H1	H2	H3	H4	L1	L2	L3	L4	L5	L6	L7	L8
VABE-S1-1R...G12	44	6	6	G1/2	G1/4	6.5	77.4	33	25.9	19.5	124	108	72	26	35	54	27	8
VABE-S1-1R...N12				1/2 NPT	1/4 NPT													
VABE-S1-2R...G34				G3/4	G1/4													
VABE-S1-2R...N34				3/4 NPT	1/4 NPT													

## Accessories

Ordering data		Pneumatic connection		Weight [g]	Pilot air supply	Part no.	Type
Width	1, 3, 5	12, 14					
<b>Left end plate</b>							
44 mm	G1/2	G1/4	400	Internal	8032662	VABE-S1-1L-G12	
				External	8032660	VABE-S1-1LZ-G12	
	1/2 NPT	1/4 NPT	400	Internal	8032663	VABE-S1-1L-N12	
				External	8032661	VABE-S1-1LZ-N12	
	G3/4	G1/4	360	Internal	8032666	VABE-S1-2L-G34	
				External	8032664	VABE-S1-2LZ-G34	
	3/4 NPT	1/4 NPT	360	Internal	8032667	VABE-S1-2L-N34	
				External	8032665	VABE-S1-2LZ-N34	
<b>Right end plate</b>							
44 mm	G1/2	G1/4	410	Internal	8032670	VABE-S1-1R-G12	
				External	8032668	VABE-S1-1RZ-G12	
	1/2 NPT	1/4 NPT	410	Internal	8032671	VABE-S1-1R-N12	
				External	8032669	VABE-S1-1RZ-N12	
	G3/4	G1/4	370	Internal	8032674	VABE-S1-2R-G34	
				External	8032672	VABE-S1-2RZ-G34	
	3/4 NPT	1/4 NPT	370	Internal	8032675	VABE-S1-2R-N34	
				External	8032673	VABE-S1-2RZ-N34	

## Accessories

### Cover plate NDV

Materials:

Width 42 mm, 52 mm, 65 mm:  
Steel

Width 76 mm:  
Wrought aluminium alloy

Dimensions → page 115



#### General technical data

Conforms to standard

ISO 5599-1

#### Operating and environmental conditions

Operating medium

Compressed air to ISO 8573-1:2010 [7:-:-]

Note on the operating/pilot medium

Lubricated operation possible (in which case lubricated operation will always be required)

#### Ordering data

Width	Weight [g]	Part no.	Type
42 mm	113	★ 9489	NDV-1-ISO
52 mm	166	11308	NDV-2-ISO
65 mm	314	10340	NDV-3-ISO
76 mm	1480	11142	NDV-4-ISO

### Isolating disc NSC

Materials:

Wrought aluminium alloy

Dimensions → 115



#### General technical data

Conforms to standard

ISO 5599-1

#### Operating and environmental conditions

Width 42 mm 52 mm 65 mm 76 mm

Note on materials Free of copper and PTFE -

#### Ordering data

Width	Pneumatic connection	Weight [g]	Part no.	Type
42 mm	G1/4	6	★ 11550	NSC-1/4-1-ISO
52 mm	G3/8	9.2	11908	NSC-3/8-2-ISO
65 mm	G1/2	20	11551	NSC-1/2-3-ISO
76 mm	G3/4	24	11699	NSC-3/4-4-ISO

Festo core product range



Generally ready for dispatch from the factory within 24 hours




Generally ready for dispatch from the factory within 5 days

## Accessories

### Duct separation VABD

Materials:  
Steel, NBR



#### General technical data

Based on standard	ISO 5599-1
Suitable for vacuum	Yes
Exhaust air function	Via throttle plate
Type of mounting	Via through-hole for M6 screw

#### Materials

Separator plate	Steel NBR
Note on materials	RoHS-compliant

#### Operating and environmental conditions

Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Pilot medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure [bar]	0 ... 10
Ambient temperature [°C]	-10 ... +50
Temperature of medium [°C]	-10 ... +50
Storage temperature [°C]	-20 ... +60
Corrosion resistance CRC <sup>1)</sup>	0
CE marking (see declaration of conformity) <sup>2)</sup>	To EU Low-Voltage Directive

1) Corrosion resistance class CRC 0 to Festo standard FN 940070

No corrosion stress. Applies to small, visually unimportant standard parts such as threaded pins, circlips and clamping sleeves which are usually only available on the market in a phosphated or burnished version (and possibly oiled) as well as to ball bearings (for components < CRC 3) and plain bearings.

2) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

#### Ordering data

Duct separation	Weight [g]	Part no.	Type
Duct 1	60	8029438	VABD-S1-1-P1-C
Duct 3 and duct 5	70	8029439	VABD-S1-1-P2-C
Ducts 1, 3 and 5	75	8029440	VABD-S1-1-P3-C
Ducts 1, 3, 5, 12 and 14	75	8029441	VABD-S1-1-P6-C
Duct 12 and duct 14	60	8036068	VABD-S1-1-P7-C

## Accessories

### Intermediate plate NZV

For connecting manifold sub-bases of different sizes

Materials:  
Die-cast aluminium, anodised





#### General technical data

Based on standard	ISO 5599-1
Note on materials	Free of copper and PTFE

#### Dimensions

NZV-1-2

Download CAD data → [www.festo.com](http://www.festo.com)




Type	B1	B2	B3	B4	D1	D2	D3	D4	H1	H2	L1	L2	L3	L4	L5	T1	T2
NZV-1-2	47	24	23	–	M6	M5	7	–	25	7.5	135	115	95	30	–	13	12
NZV-3-2/1	56	25	24	22	M6	M5	12	9	30	15	190	168	115	52	95	12	10

#### Ordering data

	Weight [g]	Part no.	Type
For manifold sub-bases of width 42 mm, 52 mm	393	164940	NZV-1-2
For manifold sub-bases of width 42 mm and 65 mm or 52 mm and 65 mm	473	12911	NZV-3-2/1

## Accessories

## Dimensions – Manifold assembly


Download CAD data → [www.festo.com](http://www.festo.com)

Width	B1	B2	B3	B4	B5	B6	B7	B8	B9	D1	D2	D3	D4	D5	D6
													Ø	Ø	Ø
42 mm	43	22	42	40	11	7.5	1.5	4	21.6	G1/4	G3/8	G1/8	10	5.5	7
52 mm	56	26	55	50	13	6	5	6	27	G3/8	G1/2	G1/8	11	6.6	9
65 mm	71	30	70	70	15	8	6	6	35.5	G1/2	G1	G1/8	15	9	12
76 mm	82	30	80	80	15	9	8	–	–	G3/4	G1	G1/8	15	9	12

Width	H1	H2	H3	H4	H5	H6	H7	L1	L2	L3	L4	L5	L6	L7	T1
42 mm	81	46	44	50.5	12.5	37	5	110	95	80	28	26	11	11	5.7
52 mm	85	47	45	60	15	40	5	135	115	96	35	30	15	14	6.8
65 mm	99	56	54	66	17.5	45	5	190	168	120	52	38	19	19	9
76 mm	120	58	55	–	–	65	5	215	184	–	56	52	–	–	9

Note: This product conforms to ISO 1179-1 and ISO 228-1.

## Accessories



Exhaust air flow control for 3 and 5.




General technical data			
Type	VABF-S1-1-F1B1-C	VABF-S1-2-F1B1-C	GRO-ZP-3-ISO
Based on standard	ISO 5599-1		
Pneumatic vertical stacking	Throttle plate, exhaust air flow control		
Mounting position	Any		
Type of mounting	With through-hole		
Standard nominal flow rate	[l/min]	1100	1500
Degree of protection		IP65	-
		NEMA4	-

Materials			
Housing	Die-cast aluminium		
Note on materials	RoHS-compliant		


Operating and environmental conditions			
Type	VABF-S1-1-F1B1-C	VABF-S1-2-F1B1-C	GRO-ZP-3-ISO
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]	Compressed air to ISO 8573-1:2010 [7:-:-]	
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)	Lubricated operation possible (in which case lubricated operation will always be required)	Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[bar]	-0.9 ... +10	-0.9 ... +10
Input pressure 1	[bar]	-	+0.5 ... +10
Ambient temperature	[°C]	-5 ... +50	-5 ... +50
Temperature of medium	[°C]	-	-20 ... +80
		-	-20 ... +80

## Accessories


**Standard nominal flow rate  $q_{nN}$  as a function of the turns  $n$  of the adjusting screw**  
VABF-S1-1-F1B1-C



VABF-S1-2-F1B1-C



GRO-ZP-3-ISO




## Accessories

### Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)


VABF-S1...



[1] Captive retaining screws

[2] Port pattern to ISO 5599-1

GRO-ZP-3-ISO




[1] Adjusting screw for flow control

[2] Captive retaining screws

Type	Width	B1	B2	B3	D1	H1	H2	H3	H4	L1	L2	L3	L5	L6	T1
VABF-S1-1-F1B1-C	42 mm	39.9	24.3	16.1	9.3	17.5	9.2	—	28	105.3	—	—	—	32	7.3
VABF-S1-2-F1B1-C	52 mm	52	32.5	22.5	13.4	29.5	13.5	—	45	131	—	—	—	40.9	10
GRO-ZP-3-ISO	65 mm	70	48	—	M8	33	12	16.5	—	132	64	32	7	—	—

### Ordering data

Circuit symbol



Description

Width


Weight  
[g]

Part no.

Type

	Exhaust air flow control	42 mm	220	549102	VABF-S1-1-F1B1-C
		52 mm	565	555788	VABF-S1-2-F1B1-C
		65 mm	850	119674	GRO-ZP-3-ISO

## Accessories



Alternative compressed air supply for port 1 of the mounted valve.



General technical data		
Type	VABF-S1-1-P1A3-G38	VABF-S1-2-P1A3-G12
Based on standard	ISO 5599-1	
Pneumatic vertical stacking	Alternative compressed air supply for 1	
Mounting position	Any	
Type of mounting	On individual sub-base, on manifold sub-base	
Standard nominal flow rate	[l/min]	1300 2800
Pneumatic connection 1	G3/8	G1/2
Degree of protection	IP65	IP65
	NEMA4	NEMA4


Materials		
Housing	Die-cast aluminium	
Note on materials	RoHS-compliant	

Operating and environmental conditions		
Type	VABF-S1-1-P1A3-G38	VABF-S1-2-P1A3-G12
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[bar]	-0.9 ... +10 -0.9 ... +10
Input pressure 1	[bar]	- +0.5 ... +10
Ambient temperature	[°C]	-5 ... +50 -5 ... +50

## Accessories

### Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)




[1] Captive screws

[2] Port pattern to ISO 5599-1

Type	B1	B2	D1	H1	H4	L1	L6	T1
VABF-S1-1-P1A3-G38	42.1	24.2	G3/8	32.7	45.3	117.6	35.8	7.9
VABF-S1-2-P1A3-G12	54	31	G1/2	42.4	58.9	136	38	10

### Ordering data

Circuit symbol



Description

Width

Standard nominal flow rate  
[l/min]

Weight

Part no.

Type

42 mm

1300

52 mm

2800

340

605


**549100**

**555785**

**VABF-S1-1-P1A3-G38**

**VABF-S1-2-P1A3-G12**

## Accessories



Vertical pressure shut-off plate for blocking duct 1 and duct 14 upstream of a valve.



General technical data		
Type	VABF-S1-1-L1D1-C	VABF-S1-2-L1D1-C
Based on standard	ISO 5599-1	
Pneumatic vertical stacking	Shut-off for 1	Alternative compressed air supply for 1
Mounting position	Any	
Type of mounting	On individual sub-base, on manifold sub-base	
Standard nominal flow rate	[l/min]	1200 1950
Pneumatic connection 1	G3/8	G1/2
Degree of protection	IP65	IP65
	NEMA4	NEMA4


Materials		
Housing	Die-cast aluminium	
Note on materials	RoHS-compliant	

Operating and environmental conditions		
Type	VABF-S1-1-L1D1-C	VABF-S1-2-L1D1-C
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)	
Operating pressure	[bar]	-0.9 ... +10 -0.9 ... +10
Input pressure 1	[bar]	- +0.5 ... +10
Ambient temperature	[°C]	-5 ... +50 -5 ... +50

## Accessories


### Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)




Type	B1	B2	D1	H1	H2	H4	L1	L6	T1
VABF-S1-1-L1D1-C	42.1	26.7	12.8	15.6	1.6	45.3	173.8	92	7.9
VABF-S1-2-L1D1-C	54	32.6	14	21.3	1.6	58.7	191.2	93.2	10

### Ordering data

Circuit symbol	Description	Width	Standard nominal flow rate [l/min]	Weight [g]	Part no.	Type
	Vertical pressure shut-off plate	42 mm 52 mm	1200 1950	600 1030	<b>549103</b> <b>555790</b>	<b>VABF-S1-1-L1D1-C</b> <b>VABF-S1-2-L1D1-C</b>

## Accessories



The pressure regulator enables a particular pressure in the regulated port to be set manually upstream or downstream of the valve.



<b>General technical data</b>			
Type	VABF-S1-1-R...	VABF-S1-2-R...	LR-ZP-...-3
Width [mm]	42	52	65
Based on standard	ISO 5599-1	ISO 5599-1	ISO 5599-1
Pneumatic vertical stacking	Pressure regulator	Pressure regulator	Pressure regulator
Design	–	–	Piston
Regulator function	Output pressure constant With secondary exhausting	Output pressure constant With secondary exhausting	–
Mounting position	Any	Any	–
Type of mounting	On individual sub-base On manifold sub-base	On individual sub-base On manifold sub-base	–
Optional pressure gauge	Possible	Possible	–
Pressure gauge connection	With retaining clamp	With retaining clamp	–
Degree of protection	IP65 NEMA4	IP65 NEMA4	–

<b>Materials</b>			
Type	VABF-S1-1-R...	VABF-S1-2-R...	LR-ZP-...-3
Regulator housing	Die-cast aluminium	Die-cast aluminium	Die-cast aluminium, steel
Control unit	PA	PA	–
Seals	–	–	NBR
Note on materials	RoHS-compliant Free from paint-wetting impairment substances	RoHS-compliant Free from paint-wetting impairment substances	RoHS-compliant Contains paint-wetting impairment substances

<b>Operating and environmental conditions</b>			
Type	VABF-S1-1-R...	VABF-S1-2-R...	LR-ZP-...-3
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]	–	–
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)	–	–
Input pressure 1 [bar]	+0.5 ... +10	+0.5 ... +10	Max. 14
Ambient temperature [°C]	-5 ... +50	-5 ... +50	–
Certification	–	–	UL – Recognized (OL)


<b>Product weight</b>			
Type	VABF-S1-1-R...	VABF-S1-2-R...	LR-ZP-...-3
Regulated port 1	640 g	1190 g	1220 g
Regulated port 2	640 g	1230 g	1220 g
Regulated port 4	640 g	1230 g	1220 g
Regulated ports 2 and 4	920 g	1990 g	1770 g

## Accessories

### Dimensions

VABF-S1-1..., VABF-S1-2...

Download CAD data → [www.festo.com](http://www.festo.com)




Type	B1	B2	H1	H2	H3	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10	T1
<b>Regulator plate, width 42 mm</b>																
VABF-S1-1-R1...	42.1	23.6	115	112	87.1	—	207.1	—	125.3	—	—	49.4	36	27	9	7.9
VABF-S1-1-R2...						—	—	216.2	125.3	—	—					
VABF-S1-1-R3...						—	—	—	125.3	150.3	216.1					
VABF-S1-1-R4...						311.6	—	—	—	—	—					
VABF-S1-1-R5...						311.6	—	—	—	—	—					
VABF-S1-1-R6...						—	—	216.2	125.3	—	—					
VABF-S1-1-R7...						—	—	—	125.3	150.3	216.1					
<b>Regulator plate, width 52 mm</b>																
VABF-S1-2-R1...	54	23.6	182	167	94.4	—	250.2	—	152.2	—	—	49.4	48	38	12	10
VABF-S1-2-R2...						—	—	264.2	152.2	—	—					
VABF-S1-2-R3...						—	—	—	152.2	180.2	264.2					
VABF-S1-2-R4...						380.4	—	—	—	—	—					
VABF-S1-2-R5...						380.4	—	—	—	—	—					
VABF-S1-2-R6...						—	—	264.2	152.2	—	—					
VABF-S1-2-R7...						—	—	—	152.2	180.2	264.2					

## Accessories

## Dimensions

LR-ZP-...-3

Download CAD data → [www.festo.com](http://www.festo.com)

[1] Pressure gauge connection  
G1/8

[3] Port pattern to ISO 5599-1

[4] Captive retaining screws

[5] Rotary knob



[2] Adjusting screw

Type	B	H	H1	H2	L1	L2	L3	L4	L5	L6	L7	L8
<b>Regulator plate, width 65 mm</b>												
LR-ZP-P-D-3	70	63	65	14	201.5	-	274	-	-	-	119	-
LR-ZP-B-D-3					201.5	-	-	-	274	72.5	-	119
LR-ZP-A-D-3					201.5	-	-	403	-	-	119	119
LR-ZP-A/B-D-3					201.5	260	-	-	-	-	119	-








Flow rate  $q_n$  as a function of output pressure  $p_2$ 

LR-ZP-A-D-3, LR-ZP-B-D-3, LR-ZP-A/B-D-3

LR-ZP-P-D-3



## Accessories

Ordering data	Regulated port	Regulator	Regulation range	Part no.	Type
<b>Regulator plate, width 42 mm</b>					
	1	P	0.5 ... 6 bar	546817	VABF-S1-1-R1C2-C-6
			0.5 ... 10 bar	546818	VABF-S1-1-R1C2-C-10
	2	B	1 ... 6 bar	546821	VABF-S1-1-R2C2-C-6
			1 ... 10 bar	546822	VABF-S1-1-R2C2-C-10
	2, reversible	B	0.5 ... 6 bar	546827	VABF-S1-1-R6C2-C-6
			0.5 ... 10 bar	546828	VABF-S1-1-R6C2-C-10
	4	A	1 ... 6 bar	546819	VABF-S1-1-R3C2-C-6
			1 ... 10 bar	546820	VABF-S1-1-R3C2-C-10
	4, reversible	A	0.5 ... 6 bar	546829	VABF-S1-1-R7C2-C-6
			0.5 ... 10 bar	546830	VABF-S1-1-R7C2-C-10
	2 and 4	AB	1 ... 6 bar	546823	VABF-S1-1-R4C2-C-6
			1 ... 10 bar	546824	VABF-S1-1-R4C2-C-10
	2 and 4, reversible	AB	0.5 ... 6 bar	546825	VABF-S1-1-R5C2-C-6
			0.5 ... 10 bar	546826	VABF-S1-1-R5C2-C-10

## Accessories

Ordering data	Regulated port	Regulator	Regulation range	Part no.	Type
<b>Regulator plate, width 52 mm</b>					
	1	P	0.5...6 bar	555757	VABF-S1-2-R1C2-C-6
			0.5...10 bar	555758	VABF-S1-2-R1C2-C-10
	2	B	1...6 bar	555759	VABF-S1-2-R2C2-C-6
			1...10 bar	555760	VABF-S1-2-R2C2-C-10
	2, reversible	B	0.5...6 bar	555767	VABF-S1-2-R6C2-C-6
			0.5...10 bar	555768	VABF-S1-2-R6C2-C-10
	4	A	1...6 bar	555761	VABF-S1-2-R3C2-C-6
			1...10 bar	555762	VABF-S1-2-R3C2-C-10
	4, reversible	A	0.5...6 bar	555769	VABF-S1-2-R7C2-C-6
			0.5...10 bar	555770	VABF-S1-2-R7C2-C-10
	2 and 4	AB	1...6 bar	555763	VABF-S1-2-R4C2-C-6
			1...10 bar	555764	VABF-S1-2-R4C2-C-10
	2 and 4, reversible	AB	0.5...6 bar	555765	VABF-S1-2-R5C2-C-6
			0.5...10 bar	555766	VABF-S1-2-R5C2-C-10



## Accessories

Ordering data	Regulated port	Regulator	Regulation range	Part no.	Type
<b>Regulator plate, width 65 mm</b>					
	1	P	0 ... 12 bar	35968	LR-ZP-P-D-3
	2	B	0 ... 12 bar	35426	LR-ZP-B-D-3
	4	A	0 ... 12 bar	35971	LR-ZP-A-D-3
	2, 4	AB	0.5 ... 12 bar	35429	LR-ZP-A/B-D-3




Ordering data – Accessories	Width	Weight [g]	Part no.	Type
Pressure gauge for intermediate pressure regulator plates LR-ZP	65 mm	64.5	345395	MA-40-16-1/8

• Note: This product conforms to ISO 1179-1 and ISO 228-1.




## Accessories

Ordering data		Description	Voltage	Cable length [m]	Part no.	Type
<b>Solenoid coil MSF</b>						
	Solenoid coil	12 V DC	–	34410	MSFG-12-OD	
		24 V DC and 42 V AC, 50 ... 60 Hz	–	34411	MSFG-2 4/42-5 0/60-OD	
		42 V DC	–	34413	MSFG-42-OD	
		24 V AC	–	34415	MSFW-24-5 0/60-OD	
		48 V AC, 50 ... 60 Hz	–	34418	MSFW-48-5 0/60-OD	
		110 V AC, 50 ... 60 Hz and 120 V AC, 60 Hz	–	34420	MSFW-110-5 0/60-OD	
		230 V AC, 50 ... 60 Hz and 240 V AC, 60 Hz	–	34422	MSFW-230-5 0/60-OD	
		240 V AC, 50 ... 60 Hz	–	34424	MSFW-240-5 0/60-OD	
	Solenoid coil with socket MSSD	12 V DC	–	4526	MSFG-12	
		24 V DC and 42 V AC, 50 ... 60 Hz	–	4527	MSFG-2 4/42-5 0/60	
		24 V AC	–	4534	MSFW-24-5 0/60	
		110 V AC, 50 ... 60 Hz and 120 V AC, 60 Hz	–	6720	MSFW-110-5 0/60	
		230 V AC, 50 ... 60 Hz and 240 V AC, 60 Hz	–	4540	MSFW-230-5 0/60	
	Solenoid coil for ATEX environment	24 V DC	1	8059804	VACF-B-K1-1-1-EX4-M	
			5	8059805	VACF-B-K1-1-5-EX4-M	
		24 V AC, 50 ... 60 Hz	1	8059808	VACF-B-K1-1A-1-EX4-M	
		110 V AC, 50 ... 60 Hz	1	8059811	VACF-B-K1-16B-1-EX4-M	
			5	8059812	VACF-B-K1-16B-5-EX4-M	
		230 V AC, 50 ... 60 Hz	1	8059809	VACF-B-K1-3A-1-EX4-M	
			5	8059810	VACF-B-K1-3A-5-EX4-M	
<b>Solenoid coil MSN1</b>						
	Solenoid coil	24 V DC	–	123060	MSN1G-24DC-OD	
		12 V DC and 24 V AC, 50 ... 60 Hz	–	170152	MSN1W-24AC/12DC	
		110 V AC, 50 ... 60 Hz	–	123061	MSN1W-110AC-OD	
		230 V AC, 50 ... 60 Hz	–	123062	MSN1W-230AC-OD	

## Accessories

Ordering data	Description		Cable length [m]	Part no.	Type
<b>Electrical accessories for solenoid coil MSF</b>					
	Angled socket	Screw terminal	Cable fitting Pg9	–	34431 MSSD-F
			Cable fitting M16	–	59710 MSSD-F-M16
		Insulation displacement technology	Cable fitting M16	–	192746 MSSD-F-S-M16
	PUR cable sheath, connection technology M12x1 A-coded	24 AC/DC	• Signal status display • Protective circuit	0.3 0.6	3679773 NEBV-B2W3F-P-K-0.3-N-M12W3 3679774 NEBV-B2W3F-P-K-0.6-N-M12W3
		110 AC/DC	–	0.3 0.6	3579463 NEBV-B2W3-K-0.3-N-M12W3 3579464 NEBV-B2W3-K-0.6-N-M12W3
			–	0.6	3679778 NEBV-B2W3F-P-K-0.6-N-LE3
		PVC cable sheath	24 AC/DC	• Signal status display • Protective circuit	0.6
			230 AC/DC	–	3579468 NEBV-B2W3-K-0.6-N-LE3
			24 V DC	Signal status display	2.5 5 10
			230 V AC	–	30935 KMF-1-24DC-2.5-LED 30937 KMF-1-24DC-5-LED 193458 KMF-1-24DC-10-LED 30936 KMF-1-230AC-2.5 30938 KMF-1-230AC-5
	Illuminating seal	12 ... 24 V DC	Signal status display	–	19143 MF-LD-12-24DC
		230 V DC/V AC	Signal status display	–	19144 MF-LD-230AC
<b>Electrical accessories for solenoid coil MSN1 and MD</b>					
	Angled socket	Screw terminal	Cable fitting Pg9	–	34583 MSSD-C
			Cable fitting M16	–	539709 MSSD-C-M16
		Insulation displacement technology	Cable fitting M16	–	192748 MSSD-C-S-M16
	PUR cable sheath, connection technology M12x1 A-coded	• 24 AC/DC	• Signal status display • Protective circuit	0.3 0.6	3679771 NEBV-A1W3F-P-K-0.3-N-M12W3 3679772 NEBV-A1W3F-P-K-0.6-N-M12W3
		110 AC/DC	–	0.3 0.6	3579461 NEBV-A1W3-K-0.3-N-M12W3 3579462 NEBV-A1W3-K-0.6-N-M12W3
			–	0.6	3679776 NEBV-A1W3F-P-K-0.6-N-LE3
		• 24 AC/DC	• Signal status display • Protective circuit	0.6	3579466 NEBV-A1W3-K-0.6-N-LE3
	PUR cable sheath	230 AC/DC	–	0.6	30931 KMC-1-24DC-2.5-LED 30933 KMC-1-24DC-5-LED 193459 KMC-1-24DC-10-LED 30932 KMC-1-230AC-2.5
		PVC cable sheath	24 V DC	Signal status display	2.5 5 10
			230 V AC	–	30934 KMC-1-230AC-5
		–	–	–	–
	Illuminating seal	12 ... 24 V DC	Signal status display	–	19145 MC-LD-12-24DC
		230 V DC/V AC	Signal status display	–	19146 MC-LD-230AC

## Accessories

Ordering data		Description	Part no.	Type	PU <sup>1)</sup>
<b>Electrical accessories for valves with central plug</b>					
	Angled socket, M12, 4-pin, type A, screw terminal	-	12956	SIE-WD-TR	1
	Modular system for connecting cables → Internet: nebu	0.1 ... 30 m	-	NEBU-...	-
	Connecting cable, straight socket, M12x1, 5-pin, open cable end, 4-wire	2.5 5	550326 541328	NEBU-M12G5-K-2.5-LE4 NEBU-M12G5-K-5-LE4	1 1
	Connecting cable, angled socket, M12x1, 5-pin, open cable end, 4-wire	2.5 5	550325 541329	NEBU-M12W5-K-2.5-LE4 NEBU-M12W5-K-5-LE4	1 1
<b>Pressure gauge</b>					
	With cartridge connection for regulator	10 bar 6 bar	543487 543488	PAGN-26-16-P10 PAGN-26-10-P10	1 1
<b>Seal</b>					
	Enables the valves with central plug M12, 3-pin, to be assembled on the sub-bases of the valve terminal VTSA/VTSA-F		571343	VABD-S2-1-S-C	2
<b>Inscription label</b>					
	Inscription label for valves		161937	IBS-9x17	24
	Clip-on inscription label holder for valve cap, for valves with central plug M12, 3-pin		540888	ASCF-T-S6	5
<b>Manual override</b>					
	Cover cap for manual override, non-detenting	For valves with central plug M12, 3-pin	541010	VAMC-S6-CH	10
	Cover cap for manual override, concealed	For valves with central plug M12, 3-pin	541011	VAMC-S6-CS	10
	Heavy-duty cover cap for manual override, non-detenting, detenting via accessory	For valves with central plug M12, 3-pin	4105147	VAMC-B-S6-CTR	10
	Tool for manual override	For MN1H/MFH valves For heavy-duty cover cap, detenting position	157651 1662543	AHB-MD/MF/MV AHB-MEB-B	1 1

1) Packaging unit

# Festo - Your Partner in Automation



## 1 Festo Inc.

5300 Explorer Drive  
Mississauga, ON L4W 5G4  
Canada

### Festo Customer Interaction Center

Tel: 1 877 463 3786  
Fax: 1 877 393 3786  
Email: [customer.service.ca@festo.com](mailto:customer.service.ca@festo.com)

## 2 Festo Pneumatic

Av. Ceylán 3,  
Col. Tequesquínáhuac  
54020 Tlalnepantla,  
Estado de México

### Multinational Contact Center

01 800 337 8669  
[ventas.mexico@festo.com](mailto:ventas.mexico@festo.com)

## 3 Festo Corporation

1377 Motor Parkway  
Suite 310  
Islandia, NY 11749

### Festo Customer Interaction Center

1 800 993 3786  
1 800 963 3786  
[customer.service.us@festo.com](mailto:customer.service.us@festo.com)

## 4 Regional Service Center

7777 Columbia Road  
Mason, OH 45040

### Connect with us



[www.festo.com/socialmedia](http://www.festo.com/socialmedia)



[www.festo.com](http://www.festo.com)