

FESTO

## **Individual devices**

Product range overview

Туре					Pressure regulation range [bar]						Input pressure [bar]				→ Page	
		G½8	G1/4	G3/8	G½	0.05 7	0.05 2.5	0.05 4	0.1 10	0.5 7	0.5 12	1 20	112	2 8	2 10	
Pressure regulators LR		•	-	-	-	-	-	-	-	•	•	•	-	-	-	3 / 4.1-0
Precision pressure regulators LRP		-	-	-	-	•	-	-	•	-	-	-	-	-	_	3 / 4.2-0
Pressure boosters <b>DPA</b>		-	-	•	•	ſ	-	-	ſ	-	_	_	_	•	•	3 / 4.7-0

Туре	Pneum	atic con	nection			Input	re	Grade of filtration		Conder drain	ısate	Supply	voltage		→ Page
	G <sup>1</sup> / <sub>4</sub>	G3/8	G½	G3/4	G1	0 16	4 10.5	0.01 mf]	1	manual rotary	fully automatic	24 V DC	110 V AC	230 V AC	
Fine and micro filters LFMB-H/LFMA-H	-	-	-	-	-	-	-	-	•	-	-	-	-	-	3 / 4.3-0
Filter combination <b>LFMBA-H</b>	-	-	•	•	•	•	-	•	-	-	•	-	-	-	3 / 4.3-5
Adsorption dryer LDF	•	-	•	-	-	-	•	-	-	-	-	•	•	•	3 / 4.5-1
Filter silencer <b>LFU</b>	-	•	-	-	•	•	-	-	_	•	_	-	-	-	3 / 4.3-11
Shut-off valve HE-LO	-	•	•	•	•	-	-	-	-	-	-	-	-	-	3 / 4.4-0

**FESTO** 


## **Individual devices**

Product range overview

Туре	Pneumatic co	nnection	Operating pre	ssure		Nominal oper	→ Page		
	G1/4	G½	[bar] 0 14	0.8 16	4 16	24 V DC	110 V AC	230 V AC	
Condensate drain <b>WA</b>	•	-	•	-	•	-	_	-	3 / 4.6-1
Condensate drain PWEA	-	•	-	•	-	•	•	•	3 / 4.6-4

نب	- (1
=	
3	Į,
=	g
ਚ	
=	5
륟	
.2	U
≗	Ų
2	Oracciira
드	۵

Туре		Pneumatic connection						Nominal size					Display unit			Red- green range	→ Page			
		M5	R1/8	R1/4	G½8	G1/4	QS4	QS6	QS8	15	23	27	40	50	63	bar	MPa	psi		
Pressure gauge DIN EN 837-1 MAEN		-	•	•	-	•	-	-	-	-	-	-	•	•	•	•	-	•	_	3 / 4.8-1
Pressure gauge DIN EN 837-1 MARG		-	•	•	-	-	-	-	-	-	-	-	•	•	•	•	•	•	•	3 / 4.8-4
Pressure gauge MA		-	•	-	•	•	_	-	_	-	•	•	•	•	•	•	•	•	-	3 / 4.8-6
Precision pressure gauge DIN EN 837-1 MAPEN		-	•	-	-	-	-	-	-	-	-	-	•	-	-	-	-	-	_	3 / 4.8-9
Pressure gauge MAQS		-	-	-	-	-	•	•	•	•	-	-	-	_	-	•	-	-	-	3 / 4.8-10
Flanged pressure gauge DIN EN 837-1 FMAEN		-	-	-	-	•	-	-	-	-	-	-	•	•	•	•	-	•	-	3 / 4.8-11
Flanged pressure gauge FMA		-	-	_	-	•	-	-	-	-	-	-	-	-	•	-	-	•	-	3 / 4.8-13
Precision flanged pressure gauge DIN EN 837-1 FMAPEN		-	-	-	-	•	-	-	-	-	-	-	-	-		•	-	•	-	3 / 4.8-14



Mounting attachments and accessories	Brief description	→ Page
Pressure gauge     MA	The pressure gauges measure pressure in bar and the psi display range or in MPa	3 / 4.8-1
Mounting bracket HR-D	For wall mounting	3 / 4.1-5
Regulator lock LRVS-G-1/s with lock plate	Prevents unintentional, and in conjunction with an LRVS padlock, unauthorised adjustment of the rotary knob	3 / 4.1-5
4 Padlock LRVS-D	Accessory for LRVS	3 / 4.1-5

ype co	des				
		LR	 1/8	 G	 7
Servi	e function				
LR	Pressure regulator				
LRS	Pressure regulator, lockable				
Pneur	natic connection				
1/8	Thread G <sup>1</sup> / <sub>8</sub>				
Versio	on code				
G	Version code				
_					
Press	ure regulation range				
7	0.5 7 bar				
	0.5 12 bar				

## Pressure regulators LR/LRS

Technical data

#### Function



Flow rate 600 ... 700 l/min

Temperature range
−10 ... +80 °C

Input pressure
1 ... 20 bar

The pressure regulator is free of paintwetting impairment substances.




- Larger design (brass housing)
- Good flow rate performance
- Precise diaphragm regulator
- Detenting regulator knob
- Identical mounting backet to D series
- Suitable for input pressures up to p1 = 20 bar
- 2 pressure regulation ranges: 0.5 ... 7 bar and 0.5 ... 12 bar

The pressure regulator maintains an essentially constant working pressure at the regulator outlet, regardless of pressure fluctuations in the compressed air network. The regulated operating pressure can be reduced by means of the built-in secondary exhaust, even without compressed air consumers.

The pressure regulator is available in two design variants:

- LR(S)-1/8-G for standard applications.
- LR(S)-1/8-G-7 for special individual cases, e.g. regulators in the pressure range up to 7 bar. This variant demonstrates optimal flow and control characteristics.

#### Panel mounting



Pressure regulation range 0.5 ... 7 bar

Pressure regulation range 0.5 ... 12 bar

General technical data			
Туре		LR(S)-1/8-G	LR(S)-1/8-G-7
Pneumatic connection		G½8	
Operating medium		Filtered compressed air, lubrica	ed or unlubricated (grade of filtration ≤40 μm)
Design		Input pressure compensated dia	phragm pressure regulator with secondary exhaust
Type of mounting		Via accessories	
		Front panel mounting, installati	on hole Ø 36.5 mm
Mounting position		Any	
Max. hysteresis	[bar]	0.2	
Input pressure	[bar]	1 20	
Pressure regulation range	[bar]	0.5 12	0.5 7

Standard nominal flow rate <sup>1)</sup> qnN [l/min]								
Pressure regulation range 0.5 7 bar	700							
Pressure regulation range 0.5 12 bar	600							

<sup>1)</sup> With 10 bar input pressure, 6 bar working pressure and  $\Delta p$  = 1 bar.


Ambient conditions		
Ambient temperature	[°C]	-10 +80
Corrosion resistance	CRC <sup>1)</sup>	2

Corrosion resistance class 2 according to Festo standard 940 070
 Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

Weights [g]		
	LR	LRS
Pressure regulator	320	420

#### Materials

Sectional view




Press	Pressure regulator							
1	Housing	Brass						
2	Knurled nut	Aluminium						
3	Rotary knob	LR: Polyacetate						
		LRS: Aluminium						
_	Seals	Nitrile rubber						

## Primary pressure compensation -

Primary pressure p1 as a function of output pressure p2


LR(S)-1/8-G(-7)



#### Secondary venting -

Output pressure p2 as a function of standard flow rate qn


LR(S)-1/8-G(-7)




4.1

## Technical data

#### Standard flow rate qn as a function of the output pressure p2







Primary pressure p1 = 7 bar

Primary pressure p1 = 7 bar

## LR(S)-1/8-G







Primary pressure p1 = 10 bar

Primary pressure p1 = 10 bar


#### LR(S)-1/8-G





Primary pressure p1 = 14 bar

Primary pressure p1 = 14 bar




Ordering data		
Connection	Pressure regulation range 0.5 7 bar	Pressure regulation range 0.5 12 bar
	Part No. Type	Part No. Type
G½8	159 506 LR-½	159 505 LR-1/8-G
lockable		
G <sup>1</sup> / <sub>8</sub>	194 695 LRS-½-G-7	194 694 LRS-1/8-G

#### Mounting bracket HR-D

for wall mounting


Material: Galvanised steel





Ordering data						
Туре	B1	B2	D1	L1	Part No.	Туре
			Ø			
Mounting bracket	42	28	36	57.5	164 936	HR-D-MINI

#### Regulator lock LRVS



Ordering data				
	Connection	Weight	Part No.	Туре
		[g]		
Regulator lock	G1/8	36	196 080	LRVS-G-1/8

#### Padlock LRVS-D


Material: Housing: Brass



Ordering data			
	Weight	Part No.	Туре
	[g]		
Padlock	120	193 786	LRVS-D

# Precision pressure regulators LRP/LRPS Peripherals overview and type codes






Mou	nting attachments and accessories	Brief description	→ Page
1	Pressure gauge MAP	The pressure gauges measure pressure in bar and the psi display range	3 / 4.8-9
2	Mounting bracket HR-1/4-P	For wall mounting	3 / 4.2-5
3	Regulator lock with lock plate LRVS-LRP-1/4	Prevents unintentional, and in conjunction with an LRVS padlock, unauthorised adjustment of the rotary knob	3 / 4.2-5
4	Padlock LRVS-D	Accessory for LRVS	3 / 4.2-5

ype cod	les				
		LRP		1/4	 0.7
Service	e function				
LRP	Precision pressure regulator				
LRPS	Precision pressure regulator, lockable				
Pneum	natic connection				
1/4	Thread G1/4				
Pressu	re regulation range				
0.7	0.05 0.7 bar				
2.5	0.05 2.5 bar		1		
4	0.05 4 bar				
10	0.1 10 bar				

## Precision pressure regulators LRP/LRPS

Technical data

#### Function




Flow rate 800 ... 2 300 l/min

Temperature range

Input pressure 1 ... 12 bar

The precision pressure regulator controls operating pressure (secondary side) with a diaphragm pilot control, which acts upon the main seat and thus achieves improved regulating characteristics.




■ Pressure hysteresis of < 0.02 bar for flow rate characteristic curve

■ Good response characteristics during rapid modification of input pressure and flow rate

**FESTO** 

■ Input pressure fluctuations are almost entirely compensated



Standard nominal flow rate <sup>1)</sup> qnN [l/min]					
Type LRP/LRPS-1/4	0,7	2,5	4	10	
Standard nominal flow rate [l/min]	800	1 800	2 000	2 300	

1) measured at p1 = 12 bar,  $\Delta$ p2 = 100 mbar


Ambient conditions		
Ambient temperature	[°C]	-10 +60
Temperature of medium	[°C]	-10 +60

4.2

weights [g]		
Туре	LRP	LRPS
Precision pressure regulator	380	470

#### Materials


Sectional view




Precision pressure regulator		LRP	LRPS
1 Housing Aluminium			
2	Knurled nut	Polycarbonate/polyamide	
3	Rotary knob	Polyacetate Aluminium	
-	Seals	Nitrile rubber	

#### Standard flow rate qn as a function of the output pressure p2


LRP/LRPS-1/4 -0.7




#### LRP/LRPS-1/4 -2.5



#### LRP/LRPS-1/4 -4



#### LRP/LRPS-1/4 -10





- 1 Input pressure p1 = 5 ... 12 bar
- 2 Input pressure p1 = 7 ... 12 bar
- 3 Input pressure p1 = 10 ... 12 bar
- 4 Input pressure p1 = 5 bar

- 5 Input pressure p1 = 7 bar
- 6 Input pressure p1 = 10 bar
- 7 Input pressure p1 = 12 bar

4.2








- 9 Output excess pressure p2 = 2 bar
- 10 Output excess pressure p2 = 4 bar

Primary pressure p1 = 10 bar


#### Standard flow rate qn as a function of output excess pressure p2




- 11 Output excess pressure p2 = 6 bar
- 12 Output excess pressure p2 = 8 bar
- 0utput excess pressure p2 = 10 bar

#### Output pressure p2 as a function of input pressure p1


Primary pressure dependence qn = 35 l/min




#### Primary pressure dependence qn = 220 l/min




#### Primary pressure dependence qn = 55 l/min




#### Primary pressure dependence qn = 340 l/min



#### Primary pressure dependence qn = 120 l/min




#### Primary pressure dependence qn = 420 l/min



## Precision pressure regulators LRP/LRPS

Technical data





Precision pressure regulator LRP	Precision pressure regulator, lockable LRPS
Part No. Type	Part No. Type
159 500 LRP- <sup>1</sup> / <sub>4</sub> -0,7	194 690 LRPS- <sup>1</sup> / <sub>4</sub> -0,7
162 834 LRP-1/4-2,5	194 691 LRPS- <sup>1</sup> / <sub>4</sub> -2,5
159 501 LRP-1/4-4	194 692 LRPS-1/4-4
159 502 LRP-1/4-10	194 693 LRPS-1/4-10
	Part No. Type  159 500 LRP-1/4-0,7  162 834 LRP-1/4-2,5  159 501 LRP-1/4-4

**FESTO** 

## 18. Precision pressure regulators LRP/LRPS


Accessories

#### 19.Mounting bracket HR

for wall mounting


Material: Galvanised steel





Ordering data		
	Part No.	Туре
Mounting bracket	159 503	HR-1/4-P

#### 20.Regulator lock LRVS-LRP



Ordering data				
	Connection	Weight [g]	Part No.	Туре
Regulator lock	G1⁄4	36	193 785	LRVS-LRP-1/4

#### 21.Padlock LRVS-D

Material: Housing: Brass



Ordering data			
	Weight	Part No.	Туре
	[g]		
Padlock	120	193 786	LRVS-D

4.3

Mounting attachments and accessories		Brief description	→ Page
,	1 Mounting bracket (2 pcs.)	The fine and micro filters are mounted on the wall using mounting	3 / 4.3-9
	LFMM	brackets LFMM	

#### Type codes LFMB Service function LFMA Micro filter LFMB Fine filter Pneumatic connection Thread G1/2 3/4 Thread G3/4 1 Thread G1 Series Series Condensate drain Fully automatic

**FESTO** 

### Fine and micro filters, LFMB-H/LFMA-H, H series

Technical data

#### Function



Fine filter function

Flow rate 1,100 ... 5,200 l/min

Temperature range -10 ... +60 °C

Input pressure 0 ... 16 bar



Various industries require fine or micro-filtered air: chemicals, food industry, etc. Festo fine and micro filters clean compressed air almost completely of any remaining minute water and oil droplets,

pharmaceuticals, process technology, together with any dirt particles.

Compressed air flows through a filter cartridge made of borosilicate fibreglass, from the inside to the outside. As the compressed air flows through the fibre tissues, large particles are prevented from passing the filtration bed by simple inertia, or are collected by collision with the fibres. to gravity.

■ Robust die-cast design

- Very high flow rates
- All filter units with automatic condensate drain and differential pressure gauge for displaying filter pollution

Separation of fine and very fine oil vapour particles and solid impurities down to 0.01 micron results from an extremely fine filter tissue. The smallest particles collect on the fibres where they form larger droplets (coalescing effect), which run off due

■ Fine and micro-filters fulfil stringent air quality requirements in accordance with ISO 8573-1

- Easy replacement of filter components
- Resistant to mineral and synthetic lubricants

The flow rate recommended for each filter must be observed in order to prevent the oil-water emulsion which has accumulated in the foam jacket from being drawn in by the compressed air. Compressed air should be pre-filtered to 5  $\mu m$  where fine filters and micro-filters are used.

General technical data								
Туре		Micro filters LFMA	licro filters LFMA			Fine filters LFMB		
Pneumatic connection		G1/2	<sup>2</sup> G <sup>3</sup> / <sub>4</sub> G1			G3/4	G1	
Design		Fibre filter				<u>.</u>	<u>.</u>	
Type of mounting		In-line installation						
		Via accessories						
Mounting position		Vertical ±5°						
Operating medium		Compressed air, fil	tered, grade of filt	ration 1 µm	Compresse	d air, filtered, grade o	grade of filtration 5 µm	
Grade of filtration	[µm]	0.01			1	1		
Residual oil content	[mg/m <sup>3</sup> ]	≤0.01			≤0.5	≤0.5		
Filter efficiency	[%]	99.9999						
Input pressure	[bar]	0 16						
Air purity classes per ISC	8573-1							
Particulate	·	1	·		2		·	
Atomised oil		2			3			

<sup>· | ·</sup> Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

## Fine and micro filters, LFMB-H/LFMA-H, H series Technical data

Standard nominal flow rate <sup>1)</sup> qnN [l/min]						
Connection	G <sup>1</sup> / <sub>2</sub>	G3/4	G1			
Micro filters LFMA	1,100	2,000	3,400			
Fine filters LFMB	1,600	3,300	5,200			

1) With 6 bar input pressure and  $\Delta p = 0.07$  bar.


Ambient conditions		
Ambient temperature	[°C]	-10 +60
Corrosion resistance	CRC <sup>1)</sup>	2

1) Corrosion resistance class 2 according to Festo standard 940 070 Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

Weights [g]					
	G1/2	G3⁄4	G1		
Micro filters LFMA	1,100	2,800	3,200		
Fine filters LFMB	1,100	2,800	3,200		

## Materials

Sectional view




Fine and micro filters					
1	Housing/bowl	Die-cast zinc			
2	Pressure gauge sight glass	Polymethylmethacrylate			
3	Pressure gauge housing	Polyamide			
-	Seals	Nitrile rubber			


**FESTO** 

## Fine and micro filters, LFMB-H/LFMA-H, H series

**FESTO** 

Technical data






Туре	B1	B2	В3	B4	D1	L1	L2	L3
LFMA-1/2-H-A LFMB-1/2-H-A	89		81		G½	294	194	
LFMA-3/4-H-A LFMB-3/4-H-A	120	65	112	39	G3/4	366	251	60
LFMA-1-H-A LFMB-1-H-A	120		112		G1	466	351	


Ordering data		
Connection	Grade of filtration 1 µm	Grade of filtration 0.01 μm
	Part No. Type	Part No. Type
G½	162 818 LFMB-½-H-A	162 815 LFMA-½-H-A
G <sup>3</sup> / <sub>4</sub>	162 819 LFMB-3/4-H-A	162 816 LFMA-3/4-H-A
G1	162 820 LFMB-1-H-A	162 817 LFMA-1-H-A

## Filter combinations LFMBA-H, H series

Peripherals overview



Mounting attachments and accessories	Brief description	→ Page
1 Mounting bracket (2 pcs.)	The filter combination is attached to the wall by means of the	3 / 4.3-9
LFMM	mounting brackets LFMM	



## Filter combinations LFMBA-H, H series

Technical data

#### **FESTO**

#### Function



- N - Flow rate 800 ... 2,600 l/min

- Temperature range -10 ... +60 °C

Input pressure 0 ... 16 bar

Various industries require fine or micro-filtered air: chemicals, pharmaceuticals, process technology, food industry, etc. Festo fine and micro filters clean compressed air almost completely of any remaining minute water and oil droplets, together with any dirt particles.



- Available as pre-assembled filter combination
- Very high flow rates
- All filter units with automatic condensate drain and differential pressure gauge for displaying filter pollution
- Fine and micro-filters fulfil stringent air quality requirements in accordance with ISO 8573-1
- Easy to replace filter components
- Resistant to mineral and synthetic lubricants

General technical data					
Туре		Filter combination LFMBA			
Pneumatic connection		G1/2	G3/4	G1	
Design		Fibre filter		·	
Type of mounting		In-line installation			
		Via accessories			
Mounting position		Vertical ±5°			
Grade of filtration	[µm]	0.01			
Residual oil content	[mg/m <sup>3</sup> ]	≤0.01			
Filter efficiency	[%]	99.9999			
Input pressure	[bar]	0 16			
Air purity classes per ISO	8573-1				
Particulate		1			
Atomised oil		2			

Standard nominal flow rate <sup>1)</sup> qnN [l/min]									
Connection G <sup>1</sup> / <sub>2</sub> G <sup>3</sup> / <sub>4</sub> G1									
LFMBAH-A	800	1,400	2,600						

1) With 6 bar input pressure and  $\Delta p = 0.07$  bar.

Ambient conditions										
Variant		G1/2	G3/4	G1						
Ambient temperature	[°C]	-10 +60								
Corrosion resistance	CRC <sup>1)</sup>	2								

- 1) Corrosion resistance class 2 according to Festo standard 940 070 Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.
- ♦ Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.


4.3

## Filter combinations LFMBA-H, H series

Technical data


Weights [g]									
	G <sup>1</sup> / <sub>2</sub>	G3/4	G1						
LFMBA	2,300	5,700	6,500						

## Materials




Fine	Fine and micro filters								
1	Housing/bowl	Die-cast zinc							
2	Pressure gauge sight glass	Polymethylmethacrylate							
3	Pressure gauge housing	Polyamide							
-	Seals	Nitrile rubber							


### Standard flow rate qn as a function of the output pressure $\Delta p1\text{--}2$




#### LFMBA-3/4-H-A



#### LFMBA-1-H-A







Туре	B1	B2	В3	B4	D1	L1	L2	L3
LFMBA-1/2-H-A	178		81		G <sup>1</sup> / <sub>2</sub>	294	194	
LFMBA-3/4-H-A	240	65	112	39	G3/4	366	251	60
LFMBA-1-H-A	240		112		G1	466	351	

 $<sup>\</sup>cdot$  |  $\cdot$  | Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Ordering data		
Connection	Part No.	Туре
G <sup>1</sup> / <sub>2</sub>	162 821	LFMBA-1/2-H-A
G <sup>3</sup> / <sub>4</sub>	162 822	LFMBA-3/4-H-A
G1	162 823	LFMBA-1-H-A

#### 32.Mounting bracket LFMM






Ordering data														
Connection							LFM	B/A	LFN	IBA			Part No.	Туре
	B1	B2	В3	D1	H1	H2	L1	L2	L1	L2	L3	L4		
G1/2	86	52	1.6	7	60	40	159	127	248	216	5	16.5	162 830	LFMM-½-H
G3/4, G1	116	68	2	9	80	60	200	157	320	277	5	16	162 831	LFMM-3/4-1-H

### 33.Connection piece LFMV

for connecting two filters





Ordering data								
Connection	B1	B2	D1	H1	H2	Н3	Part No.	Туре
G1/2	9.75	14	M3x0.5	19	15.5	16	162 832	LFMV-1/2-H
G3/4, G1	12.5	20	M4	29	26	25.5	162 833	LFMV-3/4-1-H

35.Filter cartridge LFMBP/LFMAP






Ordering data				
Connection	D1	D2	L1	Part No. Type
	Ø	Ø		
For fine filter				
G1/4	35	6.75	74	185 689 LFMBP-1/4-H
G½	48	21.7	126	162 827 LFMBP-1/2-H
G3/4	72	33	168.8	162 828 LFMBP-3/4-H
G1	72	33	268.8	162 829 LFMBP-1-H
For micro filter				
G1/4	35	6.75	74	185 688 LFMAP-1/4-H
G½	48	21.7	126	162 824 LFMAP-1/2-H
G3/4	72	33	168.8	162 825 LFMAP- <sup>3</sup> / <sub>4</sub> -H
G1	72	33	268.8	162 826 LFMAP-1-H

Filter silencers LFU FESTO

Technical data

#### Function



- N - Flow rate 4,000 ... 12,500 l/min

Temperature range -10 ... +100 °C

Input pressure 0 ... 16 bar

All exhaust air from pneumatic control systems is cleaned by the filter silencer.

Exhaust air is discharged into the atmosphere via a fine filter cartridge (degree of filtration: >99.99%). At the same time, exhaust noise is greatly reduced. Condensate is collected in the lower plastic bowl and can be discharged via the condensate drain.



- Exhaust air is up to 99.99% free of oil and other contaminants.
- Condensate drain, manual rotary.

■ The silencer reduces exhaust noise regardless of frequency.

General technical data							
Size		G1/4	G3/8	G <sup>1</sup> / <sub>2</sub>	G1		
Pneumatic connection		G1/4	G3/8	G½	G1		
Mounting position		Vertical ±5°					
Flow rate <sup>1)</sup>	[l/min]	≥4,000	≥4,700	≤6,000	≤12,500		
Input pressure	[bar]	0 16					
Noise reduction <sup>1)</sup>		Reduction of 40 db(A)		>40 db(A)			

- 1) At 6 bar with respect to atmosphere.
- Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Ambient conditions			
Ambient temperature	[°C]	-10 +60	0 +100
Corrosion resistance	CRC <sup>1)</sup>	2	


1) Corrosion resistance class 2 according to Festo standard 940 070 Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

Weights [g]										
Size	G <sup>1</sup> / <sub>4</sub>	G3/8	G1/2	G1						
Filter silencer	190	190	570	1,010						

## Filter silencers LFU

Technical data

**FESTO** 



Download CAD data → www.festo.com/en/engineering


Connection	D1	D2	H1	H2	=©1	Part No.	Туре	
G <sup>1</sup> / <sub>4</sub>	G1⁄4	77	131	7	26	539 132	LFU-1/4	- <b>⊙</b> - New
G3/8	G3/8	77	131	7	26	539 133	LFU-3/8	-O- New
G <sup>1</sup> / <sub>2</sub>	G1/2	90	180	12	41	10 494	LFU-1/2	
G1	G1	100	252	15	50	10 495	LFU-1	

 $<sup>\</sup>cdot$  |  $\cdot$  | Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

#### Filter cartridge LFPU

Note on material: Free of copper and PTFE






Dimensions and ordering data									
For connection	D1	D2	L1	Part No.	Туре				
	Ø	Ø							
G1/4,3/8	60	28	69	539134	LFPU-1/4-3/8 • New				
G <sup>1</sup> / <sub>2</sub>	70	34.8	110	10 496	LFPU-1/2				
G1	82	42.8	180	10 497	LFPU-1				

### Shut-off valve HE-LO, to safety standard

Technical data



#### Function



Flow rate 5,200 ... 12,000 l/min

Temperature range -10 ... +60 °C

Operating pressure 1 ... 10 bar



- Note

The shut-off valve may not be used as an emergency stop valve.

For units that require a pneumatic shut-off in order to carry out maintenance or repair work, for example.

The valve is installed into the air supply line and fulfils requirements set forth by OSHA 29 CFR 147, "Controlling Dangerous Energy Sources", issued by the United States Department of Labor.

#### Function:

The valve is used for shutting off the compressed air supply, while simultaneously exhausting systems which are powered using compressed air.

Flow from port 1 to port 2 is blocked when the actuator knob is pressed, and flow from port 2 to port 3 is opened.

The largest exhaust flow rate is achieved by keeping the actuating knob in the actuated position until the connected system is completely exhausted.

The valve can be locked in the closed position using a padlock.
This ensures that a decommissioned system (e.g. during maintenance work) cannot be pressurised without authorisation.

General technical data	General technical data						
Туре		HE-G3/8-LO	HE-G <sup>1</sup> / <sub>2</sub> -LO	HE-G3/4-LO	HE-G1-LO		
Design		Manually actuated 3/2-way va	Manually actuated 3/2-way valve with piston slide				
Type of mounting		Screwed into piping					
		2 through holes in housing with $\varnothing$ 8 mm for wall mounting					
Mounting position		Any, but make sure there is easy access to the actuating knob					
Connection	1, 2	G3/8	G1/2	G3/4	G1		
(Female thread)	3	G1					
Operating pressure	[bar]	1 10	10				

Standard nominal flow rate <sup>1)</sup> qnN [l/min]							
Connection   G3/8   G1/2   G3/4   G1							
1 2	5,200	6,200	8,000	10,000			
2 ÷ 3	12,000	2,000					

1) Measured at primary pressure pl = 6 bar and  $\Delta p$  = 1 bar.

Ambient conditions		
Ambient temperature	[°C]	-10 +60
Corrosion resistance	CRC <sup>1)</sup>	3

1) Corrosion resistance class 3 according to Festo standard 940 070 Components requiring higher corrosion resistance. External visible parts in direct contact with industrial atmospheres or media such as solvents and cleaning agents, with a predominantly functional requirement for the surface.


Weights [g]				
	G3/8	G1/2	G3/4	G1
HELO	1,100		1,000	


 $<sup>\|\</sup>cdot\|$  Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

**FESTO** 

## Shut-off valve HE-LO, to safety standard

Technical data





Туре	D1	
HE-G3/8-LO	G3/8	
HE-G <sup>1</sup> / <sub>2</sub> -LO	G <sup>1</sup> / <sub>2</sub>	
HE-G3/4-LO	G <sup>3</sup> / <sub>4</sub>	
HE-G1-LO	G1	

 $\cdot$   $\|\cdot$   $\,$  Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Ordering data		
Connection	Part No.	Туре
G3/8	197 133	HE-G3%-LO
G <sup>1</sup> / <sub>2</sub>	197 134	HE-G½-LO
G <sup>3</sup> / <sub>4</sub>	197 135	HE-G3/4-LO
G1	197 136	HE-G1-LO

# **Shut-off valve HE-LO, to safety standard** Accessories

**FESTO** 

#### 43.Padlock LRVS-D for shut-off valve

Material: Housing: Brass



Ordering data		
	Weight	Part No. Type
	[g]	
Padlock	120	193 786 LRVS-D



#### Small unit - big effect

Cold-regenerating adsorption dryer with defined pressure dew point and high flow rate for decentralised compressed air drying.

The LDF adsorption dryer effectively prevents corrosion, wear, excessive product wastage, frequent maintenance and damage to sensitive

- The solution for dry and clean compressed air
- Greater service life of pneumatic components
- Pressure dew point -40 °C, (-70 °C on request)
- Additional filtering of oil and particulate
- Produced for decentralised compressed air drying
- High flow rate performance up to 1,600 l/min
- Low energy consumption and noise levels
- In combination with a prefilter and secondary filter, this achieves air purity class 2.2.1 or 2.1.1 to DIN ISO 8573-1 at the outlet.
- Of particular interest for printed circuit production, optical industries, foil production, dental technology, drying and transportation of powder materials, paint systems, drying and cleaning precision parts, food industry and pharmaceuticals.

#### Decentralised drying

machinery.

Partial drying is already started in the after-cooler. Actual drying can be centralised in the compressor room or decentralised as required with the

consuming devices using compact Festo LDF-H-... adsorption dryers. Decentralised drying is advantageous because only the actually required amount of dry air is prepared.

Pressure dew points of less than 0 °C always require the utilisation of adsorption dryers.

#### Constant air quality

The drying granulate is introduced into the dryer in such a way as to ensure even and compact filling.

## Adsorption dryer LDF Key features and type code


Reduces energy costs  The dryers have a low differential pressure.	Reduced service costs  The dryer granulate has a long service life (approx. 15,000 operating hours).  When refilling the dryer, the Festo	filling funnel must be used to ensure that the filling density in the chambers is optimal.	Complete drying package  These dryers are fitted as standard with coalescing filters.
Function			
The airflow is filtered in the inlet filter (oil would considerably reduce the granulate service life). The adsorption dryer consists of two chambers filled with drying agent. Moist compressed air flows through the two chambers alternately, and the water from the air accumulates on the surface of the drying agent. After a predetermined period of time, the flow of air is	switched to the other chamber and a portion of the dried air is used to regenerate the drying agent in the first chamber. The drying agent has a service life of several years. The standard LDF dryers achieve a pressure dew point of -40 °C (air purity class 2.2.1 to DIN ISO 8573-1 at the outlet).	An appropriate drying agent is used with dryers which have a pressure dew point of up to -70 °C (air purity class 2.1.1 to DIN ISO 8573-1 at the outlet) (upon request). The pressure dew point should be about 10 °C less than the anticipated ambient temperature. The application area for the adsorption dryer is decentralised compressed	air preparation. The purge air requirement at the optimal operating point (6 bar/35 °C) is approx. 22%. If the dryer is used under different operating conditions, the input air/purge air ratio may change as the purge air consumption is only dependent on the input air and not on the used output flow rate.
Important			
The supplied inlet filter, a 0.01 µm micro filter, provides clean operating air. It protects the drying agents from contaminating dirt and oil particles.	The outlet filter, a 1 µm fine filter, removes any drying agent particles. The inlet filter cannot remove gaseous	components, such as water and oil vapour, from the air. However, this is achieved by the highly porous drying	granulate. It is for this reason that the LDF-H dryer achieves the highest air quality class for particles and oil.

Type code	S						
		LDF	 H1	$-\lceil$	1/4	-	24
Basic fu	nction						
LDF	Adsorption dryer						
Differen	tial pressure [mbar]						
H1	50						
H2	150						
H3	500						
H4	250						
H5	350						
Н6	600						
H7	900						
	tic connection						
1/4	Thread G <sup>1</sup> / <sub>4</sub>						
1/2	G½ thread						
Voltage							
24	24 V DC				·		
110	110 V AC						
230	230 V AC						

**FESTO** 

# Adsorption dryer LDF Technical data

Function



- N - Flow rate 26 ... 1,600 l/min

Temperature range 2 ... 50 °C

Input pressure 4 ... 10.5 bar



General technical data										
		H1	H2	Н3	H4	H5	Н6	H7		
Pneumatic connection	G1/4			G <sup>1</sup> / <sub>2</sub>						
Operating medium		Compresse	ed air, filtered, ur	llubricated						
Design	Cold regen	erating compress	sed air adsorption o	dryer						
Type of mounting	Through-h	ole								
Mounting position	Vertical ±5	0								
Pressure dew point	[°C]	-40 (-70 (	on request)							
Differential pressure	[mbar]	50	150	500	250	350	600	900		
Input pressure	[bar]	4 10.5	410.5							
Air purity class at the o	utlet	2.2.1 to DI	2.2.1 to DIN ISO 8573-1 (2.1.1 to DIN ISO 8573-1 upon request)							
		<u>'</u>								
Electrical data										
Electrical connection		With plug	socket to DIN 43	650 type A	With scre	With screw terminals				
		(MSSD-C =	(MSSD-C → Volume 2)							
Power consumption	DC	2.5 W			5 W	5 W				
	AC	50 Hz: 5 V	A		110 V:	110 V: 0.27 A				
		60 Hz: 3.7	VA		230 V:	230 V: 0.12 A				
Protection against pola	rity reversal	At 24 V DC	At 24 V DC							
CE symbol		EU directiv	EU directive 89/336/EEC Electromagnetic compatibility (all types)							
	73/23/EEC	Low voltage (all	types except LDF	24)						
Protection class		IP65 to DII	N 40 050	· · · · · · · · · · · · · · · · · · ·						

Ambient conditions								
Variant		H1	H2	H3	H4	H5	H6	H7
Media temperature	[°C]	2 50						
Ambient temperature	[°C]	2 50						
Storage temperature	[°C]	-20 +60						
Corrosion resistance	CRC <sup>1)</sup>	1						

1) Corrosion resistance class 1 according to Festo standard 940 070 Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.


Weights [g]									
	H1	H2	H3	H4	H5	H6	H7		
Adsorption dryer	5,400	6,500	9,200	24,700	30,200	35,700	41,200		

Please do not use the average consumption values as your guide when setting up the dryer, instead use


- a) the inlet pressure of the dryer
- the peak value for the flow rate
- the maximum permissible inlet temperature.

The adsorption dryers are designed for continuous operation. Pulsed or intermittent operation can lead to the premature aging of and/or damage to the drying agent and thus to the failure of the dryer.

If the adsorption dryer LDF is nonetheless to be used in pulsed or intermittent mode the use of buffer reservoirs, through which the compressed air flows, is recommended. Depending on the application these can be mounted before and/or after the dryer.




The pressure reservoirs may not be connected on one side only:



Standard non	inal flow rate qnN [Nl/m	in] at pressure d	ew point –40 °C							
Туре	Temperature of	Input pressur	Input pressure [bar]							
	medium	4	5	6	7	8	10			
LDF-H1	20 °C	25.9	40.1	57.4	65.6	73.8	90.1			
	35 °C	25.2	39.1	57.8	66.1	74.3	90.8			
LDF-H2	20 °C	51.7	80.2	114.8	131.2	147.6	180.3			
	35 °C	50.4	78.2	115.7	132.1	148.6	181.6			
				ľ	T		ľ			
LDF-H3	20 °C	111.9	173.6	248.8	284.3	319.8	390.7			
	35 ℃	109.1	169.3	250.6	286.4	322.1	393.6			
				-	-	-	-			
LDF-H4	20 °C	207.8	322.3	461.5	527.2	593.0	724.6			
	35 ℃	202.7	314.4	464.8	531.1	597.4	729.9			
LDF-H5	20 °C	273.8	424.8	607.7	694.3	781.0	954.2			
	35 °C	267.1	414.3	612.1	699.4	786.7	961.2			
LDF-H6	20 °C	359.7	558.0	799.2	913.1	1,027.1	1,255.0			
	35 ℃	350.9	544.3	805.0	919.8	1,034.6	1,264.1			
LDF-H7	20 °C	456.1	707.5	1,013.0	1,157.4	1,301.9	1,590.7			
	35 °C	444.9	690.1	1,020.4	1,165.9	1,311.3	1,602.3			

# Adsorption dryer LDF Technical data



Туре	L1	L2	L3
H1	403	186	-
H2	498	281	-
H3	738	521	-
H4	780	382	93.5
H5	946	548	176.5
H6	1,111	713	259
H7	1,176	778	341.5

Ordering data	Ordering data						
Туре	Connection	24 V DC	110 V AC	230 V AC			
		Part No. Type	Part No. Type	Part No. Type			
H1	G1/4	178 516 LDF-H1-G <sup>1</sup> / <sub>4</sub> -24 <sup>1)</sup>	178 517 LDF-H1-G <sup>1</sup> / <sub>4</sub> -110 <sup>1)</sup>	178 518 LDF-H1-G <sup>1</sup> / <sub>4</sub> -230 <sup>1)</sup>			
H2		178 519 LDF-H2-G <sup>1</sup> / <sub>4</sub> -24 <sup>1)</sup>	178 520 LDF-H2-G <sup>1</sup> / <sub>4</sub> -110 <sup>1)</sup>	178 521 LDF-H2-G <sup>1</sup> / <sub>4</sub> -230 <sup>1</sup> )			
H3		178 522 LDF-H3-G <sup>1</sup> / <sub>4</sub> -24 <sup>1)</sup>	178 523 LDF-H3-G <sup>1</sup> / <sub>4</sub> -110 <sup>1)</sup>	178 524 LDF-H3-G <sup>1</sup> / <sub>4</sub> -230 <sup>1)</sup>			
H4	G <sup>1</sup> / <sub>2</sub>	178 525 LDF-H4-G <sup>1</sup> / <sub>2</sub>	-	-			
H5		178 528 LDF-H5-G <sup>1</sup> / <sub>2</sub>	-	-			
H6		178 531 LDF-H6-G <sup>1</sup> / <sub>2</sub>	-	-			
H7		178 534 LDF-H7-G <sup>1</sup> / <sub>2</sub>	-	-			

<sup>1)</sup> Free of copper, PTFE and silicone

### 50.Drying agent LDF-TM

Drying agent: Aluminium oxide

Ordering data									
Weight	Dryer ty	pe (volun	ne requir	ed)				Part No.	Туре
[g]	H1	H2	Н3	H4	H5	Н6	H7		
1,000	1	1	2	-	2	-	2	538 661	LDF-TM-H1-H7-1KG
4,000	-	-	-	1	1	2	2	538 662	LDF-TM-H1-H7-4KG

#### 51.Funnel LDF-FS


Ordering data		
Туре	Part No.	Туре
H1 H3	538 668	LDF-FS-H1-H3
H4 H7	538 669	LDF-FS-H4-H7

#### 52.Seal range LDF-DS

Ordering data		
Туре	Part No.	Туре
H1 H3	538 670	LDF-DS-H1-H3
H4 H7	538 671	LDF-DS-H4-H7

### 53.Filter cartridge LFMBP/LFMAP





Ordering data	Ordering data							
Dryer type	Connection	Grade of filtration [µm]	D1 Ø	D2 Ø	L1	Part No.	Туре	
For inlet filter								
H1 H3	G1/4	0.01	35	6.75	74	185 688	LFMAP-1/4-H	
H4 H7	G½	0.01	48	21.7	126	162 824	LFMAP-1/2-H	
For outlet filter	For outlet filter							
H1 H3	G1/4	1	35	6.75	74	185 689	LFMBP-1/4-H	
H4 H7	G <sup>1</sup> / <sub>2</sub>	1	48	21.7	126	162 827	LFMBP-1/2-H	

#### Condensate drain WA

Technical data

#### Function



Temperature range 0 ... +60 °C

Input pressure 0 ... 16 bar



- Note

In order to close, the automatic condensate drain type WA-2 requires a flow rate of 125 l/min; this sets in at approx. 1.5 bar.

For attachment to service units and compressed air networks/systems. Condensate present in the compressed air is separated in suitable filters. The condensate that accumulates must be emptied from time to time, as otherwise it would be drawn in and could lead to faults in the downstream elements. The devices shown perform this task automatically.

They contain a float which opens when a certain condensate level is achieved. The accumulated condensate is then emptied.

With an additional, installed manual override, condensate emptying can also be performed manually.

- Automatic emptying after the max. fill level has been reached
- Automatic emptying after the operating pressure p < 0.5 bar is switched off
- Manual actuation during operation is possible


General technical data						
Туре	WA-1-B	WA-2				
Pneumatic connection	M9	M9				
Condensate drain connection	G1/4	PK-4				
Design	External, mechanically-operated, fully automatic condensate drain valve					
Operating medium	Water					
Type of mounting	In-line installation					
Mounting position	Vertical, ±10°	Vertical, ±5°				
Input pressure [bar]	4 16	0 14				
Valve function	2/2-way single solenoid valve, closed	2/2-way single solenoid valve, open				
Manual override facility	Pushing					

Ambient conditions					
Туре		WA-1-B	WA-2		
Ambient temperature	[°C]	0 +60	0 +50		
Temperature of medium	[°C]	0 +60	0 +50		
Corrosion resistance	CRC <sup>1)</sup>	2			

1) Corrosion resistance class 2 according to Festo standard 940 070 Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

Weights [g]					
	WA-1-B	WA-2			
Condensate drain	210	92			


#### Materials Sectional view



Conc	lensate drain	WA-1-B	WA-2
1	Housing	Brass	Brass
2	Float	Polypropylene	Polyacetate
3	Cover	Polyamide	Wrought aluminium
			alloy
4	Bowl	-	Polycarbonate
-	Seals	Nitrile rubber	Nitrile rubber


#### Actuating force F for manual actuation as a function of supply pressure p

WA-1-B



Primary pressure p1 = 7 bar


#### WA-2




Primary pressure p1 = 7 bar

#### Max. possible condensate flow rate Q as a function of input pressure p

WA-2



Primary pressure p1 = 7 bar



Ordering data		
Туре	Part No.	Туре
WA-1-B	158 497	WA-1-B
WA-2	152 810	WA-2

**Condensate drain PWEA** 

**FESTO** 

Technical data

#### Function



Temperature range +1 ... +60 °C





Condensate passes through the port in the bottom of the filter bowl into the attached condensate drain valve, where it is collected in a reservoir. A capacitive sensor detects once the maximum filling level is reached. The condensate escapes into the atmosphere via the opening diaphragm valve through the discharge line. The diaphragm valve closes again after a specified response time. A residual amount of condensate remains in the reservoir so that no compressed air can escape into the discharge line.

- Fully automatic condensate drain with integrated electrical control system
- Interface for communicating with master control device
- Reliable thanks to contactless capacitive sensor
- Can be used with service units or simply in piping systems
- Operated via touch-sensitive keys or electrical interface
- Ready status and switching status indicated via LEDs and electrical interface

General technical data								
		PWEA-AP-3D	PWEA-AC-6A	PWEA-AC-7A	PWEA-AC-3D			
Pneumatic connection		G½	G½					
Condensate drain connection	า	PK-8						
Design		Fully automatic condensat	e drain valve with electri	cal control interface				
Operating medium		Compressed air						
Type of mounting		In-line installation						
Mounting position		Vertical ±5°						
Operating pressure	[bar]	0.8 16.0						
Valve function 3/2-way single			2-way single solenoid valve, closed					
Manual override facility		Pushing						
Electrical								
Nominal operating voltage	[V DC]	24	-	_	24			
	[V AC]	=:	110	230	-			
Electrical connection		M12x1 plug, 5-pin	Cable conduit fitting	g Pg9				
Nominal power of	[W]	2						
condensate drain								
Alarm output	Alarm output Contacting							
Protection class (IEC 60529)		IP65						
Electrical protection class		III	II	II	III			

Ambient conditions		
Ambient temperature	[°C]	+1 +60
Temperature of medium	[°C]	+1 +60
Corrosion resistance class	CRC <sup>1)</sup>	2

<sup>1)</sup> Corrosion resistance class 2 according to Festo standard 940 070 Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.


**FESTO** 

### **Condensate drain PWEA**


Technical data

Materials					
Housing	Plastic				
Condensate reservoir	Wrought aluminium alloy				
Seals	Nitrile rubber, fluorocarbon rubber				
Note on materials	Free of copper, PTFE and silicone				

Weight [g]	
PWEA	700



Ordering data								
Part No.	Туре							
538 678	PWEA-AP-3D							
538 679	PWEA-AC-6A							
538 680	PWEA-AC-7A							
538 681	PWEA-AC-3D							



Mou	nting attachments and accessories	Brief description	→ Page
1	Pressure gauge set	The pressure gauge set is used to monitor the input and high	3 / 4.7-5
	MA-SET	pressure	
2	Silencers	The silencers are provided to reduce noise at the valve exhaust port	3 / 4.7-5
	U		
3	Foot mounting	The pressure booster can be attached to other machine parts by	3 / 4.7-5
	HUA	means of the two foot mountings	
4	Regulator lock	Prevents unintentional, and in conjunction with an LRVS padlock,	3 / 4.7-6
	LRVS with lock plate	unauthorised adjustment of the rotary knob	
5	Padlock	Accessory for LRVS	3 / 4.7-6
	LRVS-D		

Type codes						
		DPA		63	-	16
Basic fun	nction		.			
DPA	Pressure boosters					
Piston $\varnothing$	(mm)					
63						
100						
Output pressure [bar]						
10	4 10					
16	4 16					

#### Pressure boosters DPA

Technical data

#### Function











#### Note

Pressure boosters do not replace a compressor, but are intended for the occasional boosting of compressed air.



The regulator is supplied with a non-compressed regulator spring. After the input pressure is applied, the regulator spring is pretensioned by turning the regulating knob until the desired output pressure is achieved. A pressure gauge is strongly recommended to monitor the output pressure. The regulator setting can be secured against unauthorised adjustment by means of a regulator lock.

The pressure booster is a twin-piston pressure intensifier that can compress air

air.
When the DPA is pressurised with compressed air, integrated directional control and non-return valves automatically facilitate pressure build-up on the secondary side up to twice the normal operating pressure, depending on the flow rate.
The air supply to both drive pistons is controlled by a pneumatic directional control valve, which reverses automatically when the stroke endposition is reached.
The output pressure is freely selectable; it lies between the system pressure and the maximum double

value.

The reference value is set using a manually operated regulator, which supplies compressed air to the working pistons on the secondary side and ensures stable operation of the booster.

The booster starts automatically when the system pressure is applied and the desired output pressure has not yet been reached.

When the output pressure is reached, it stops operating automatically but restarts if the pressure drops again.

All benefits at a glance

- Any mounting position
- Long service life
- Compact construction and good design
- Mounting option with components from the ADVU standard range
- Minimal loss of volume with valve activation
- Short filling times

General technical data									
Туре		DPA-63-10	DPA-100-10	DPA-63-16	DPA-100-16				
Pneumatic connection		G3/8	G3/8	G <sup>1</sup> / <sub>2</sub>					
Operating medium		Compressed air, filtered, unlubricated, grade of filtration 5µm							
Design		Twin-piston pressure intensifier							
Mounting position		Any							
Input pressure p1	[bar]	2 8		2 10					
Output pressure p2	[bar]	4 10 <sup>1)</sup>		4 16 <sup>1)</sup>					
Pressure indicator		G½ prepared	G1/4 prepared	G½ prepared	G <sup>1</sup> / <sub>4</sub> prepared				

- 1) The differential pressure between the input and output pressure must be at least 2 bar.
- $\parallel$  Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Ambient conditions							
Ambient temperature	[°C]	+5 +60					
Corrosion resistance	CRC <sup>1)</sup>	2					


<sup>1)</sup> Corrosion resistance class 2 according to Festo standard 940 070 Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.


Weights [g]									
	DPA-63-10	DPA-100-10	DPA-63-16	DPA-100-16					
Pressure boosters	6,000	13,000	6,000	13,000					

Recommended tubing									
	For input pressure	For output pressure							
DPA-63	PAN-16x2	PAN-12x1,75							
DPA-100	P-19	PAN-16x2							
	PAN-16x2								


## Materials Sectional view 4 5 1 2 3 6 7 8


Pres	sure boosters	
1	Plug cap	Aluminium
2	Round nut	Galvanised steel
3	Valves	Die-cast aluminium, polyacetate
4	Rotary knob	Acetal
5	Protective cover	Acrylic butadiene styrene
6	Centre bit	Aluminium
7	Housing	Die-cast zinc
8	Cylinder barrel	Aluminium
-	Seals, regulator	Nitrile rubber
-	Seals, valve	Nitrile rubber





#### DPA-100





Туре	АН	B1	B2	В3	B4	BG	D1 Ø	E	EE	H1	H2
DPA-63-10 DPA-63-16	56.5	187	92.5	70	266	25		88	G3/8	169	62
DPA-100-10	81	244	133	102	352	30	41	128	G¹/2	244	71
DPA-100-16	01	244	155	102	222	30		120	G-/2	244	/ 1

Туре	Н3	H4	L1	L2	L3	L4	L5	L6	RT	TG	SA
DPA-63-10	17.5	60	289	122		40	19	161		62	343
DPA-63-16	17.5	00	209	122		40	17	101	M10	02	545
DPA-100-10	27	73	367	145.5	6	55	11	175	INITO	103	433
DPA-100-16	21	/3	707	143.3		25	11	1/5		103	433


 $<sup>\</sup>cdot \parallel \cdot \>\>\>$  Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Ordering data		
	Output pressure 4 10 bar	Output pressure 4 16 bar
Size	Part No. Type	Part No. Type
63	184 518 DPA-63-10	193 392 DPA-63-16
100	184 519 DPA-100-10	188 399 DPA-100-16

#### Foot mounting HUA

Material: Galvanised steel Free of copper, PTFE and silicone





Ordering data										
Size	AB	AH	AO	AT	AU	SA	TR	US	Part No.	Туре
	Ø									
63	11	56.5	11.75	6	27	343	62	85.5	157 315	HUA-63
100	13.5	81	11.75	8	33	433	103	126.5	157 317	HUA-100


#### Pressure gauge set DPA-MA

If the pressure gauge scale is to be specifically aligned, PTFE sealing tape must be used instead of the included sealing rings.

Material:

Housing: Acrylic butadiene styrene Window shield: Polystyrene Connection piece: Brass





Ordering data					
Size	D1	H1	L6	Part No.	Туре
	Ø				
63-10	41	60	161	526 096	DPA-63-10-MA-SET
63-16	41	60	101	526 097	DPA-63-16-MA-SET
100-10	41	73	175	526 098	DPA-100-10-MA-SET
		75	1/3	526 099	DPA-100-16-MA-SET


#### Silencer U

Material:

Housing: Die-cast aluminium Insert: Polyethylene

Free of copper, PTFE and silicone






Ordering data							
Connection	D	D1	L	L1	₩	Part No.	Туре
G <sup>3</sup> / <sub>8</sub>	25	G3/8	88.5	10.5	19	6843	U-3/8-B
G <sup>1</sup> / <sub>2</sub>	28	G <sup>1</sup> / <sub>2</sub>	120	14	24	6844	U-1/2-B

Core Range

### Regulator lock LRVS

Material: Cap: Polyacetate Lock plate: Steel Knurled nut: Aluminium





Ordering data			
Size	Weight	Part No.	Туре
	[g]		
63	40	193 781	LRVS-D-MINI <sup>1)</sup>
100	60	193 782	LRVS-D-MIDI <sup>1)</sup>

1) Free of copper, PTFE and silicone

#### Padlock LRVS-D

Material: Housing: Brass



Ordering data			
	Weight [g]	Part No.	Туре
Padlock	120	193 786	LRVS-D

# Pressure gauge MA, DIN EN 837-1 Technical data

**FESTO** 

Function









Technical data							
Nominal size	40	50	63				
Pneumatic connection	R <sup>1</sup> /8, G <sup>1</sup> /4, R <sup>1</sup> /4	G <sup>1</sup> / <sub>4</sub>	G <sup>1</sup> / <sub>4</sub>				
Operating medium	Liquid media						
	Gaseous media						
	Not permitted: Oxygen						
	Not permitted: Acetylene						
Design	Bourdon tube pressure gauge						
Conforms to	DIN EN 837-1						
Type of mounting	Can be screwed in						
Connection position	Centre, rear side						
Ambient temperature [°C]	-20 +60						
Accuracy of measurement, class	2.5						
Factor, continuous load	0.75						
Factor, intermittent load	0.66						
Protection class	IP43						
For MS series service units	MS4/MS6	-	-				
Materials	Housing: Acrylic butadiene styrene						
	Window shield: Polystyrene						
	Threaded plug: Brass						
Weight [g]	60	70	80				

Indicating range								
[bar]	[psi]	40	50	63				
0 1	0 14.5	-	-					
0 2.5	0 36	-						
0 6	0 87	•	-	_				
0 10	0 145	•						
0 16	0 232	•						
0 25	0 360		-	-				





Туре	D1 ∅	L1	L2
MA-50	49	47.5	26.5
MA-63	61.5	48.5	27.5

Individual units Pressure gauges

# Pressure gauge MA, DIN EN 837-1 Technical data

Nominal size	Pneumatic	Indicating range	Part No. Type	
connection	[bar]	[psi]		
40	R <sup>1</sup> /8	0 10	0 145	162 835 MA-40-10-1/8-EN
		0 16	0 232	162 836 MA-40-16- <sup>1</sup> / <sub>8</sub> -EN
		0 25	0 360	526 167 MA-40-25-1/8-EN
40	G <sup>1</sup> / <sub>4</sub>	0 6	0 87	183 899 MA-40-6-G <sup>1</sup> / <sub>4</sub> -EN
		0 10	0 145	183 900 MA-40-10-G <sup>1</sup> / <sub>4</sub> -EN
		0 16	0 232	183 901 MA-40-16-G <sup>1</sup> / <sub>4</sub> -EN
		0 25	0 360	183 902 MA-40-25-G <sup>1</sup> / <sub>4</sub> -EN
40	R1/4	0 6	0 87	187 078 MA-40-6-R <sup>1</sup> / <sub>4</sub> -EN
		0 10	0 145	187 079 MA-40-10-R <sup>1</sup> / <sub>4</sub> -EN
		0 16	0 232	187 080 MA-40-16-R <sup>1</sup> / <sub>4</sub> -EN
		0 25	0 360	187 081 MA-40-25-R <sup>1</sup> / <sub>4</sub> -EN
50	G1/4	0 2.5	0 36	162 837 MA-50-2,5-1/4-EN
		0 10	0 145	162 838 MA-50-10- <sup>1</sup> / <sub>4</sub> -EN
		0 16	0 232	162 839 MA-50-16- <sup>1</sup> / <sub>4</sub> -EN
63	G <sup>1</sup> / <sub>4</sub>	0 1	0 14.5	162 844 MA-63-1- <sup>1</sup> / <sub>4</sub> -EN
		0 2.5	0 36	162 845 MA-63-2,5- <sup>1</sup> / <sub>4</sub> -EN
		0 10	0 145	162 840 MA-63-10-1/4-EN
		0 16	0 232	162 841 MA-63-16- <sup>1</sup> / <sub>4</sub> -EN

### Pressure gauge MA, DIN EN 837-1, with red-green range

**FESTO** 

Technical data

Function







The adjustable red-green range provides additional safety when monitoring compressed air.

With the two red segments above the pressure gauge scale along with the printed green segment it is possible to individually limit the desired pressure range.

This coloured demarcation enables you to recognise immediately whether or not the pressure is in the permitted tolerance range.

Technical data						
Nominal size	40	50	63			
Pneumatic connection	R <sup>1</sup> /8	R1/4	R1/4			
Operating medium	Liquid media					
	Gaseous media					
	Not permitted: Oxygen					
	Not permitted: Acetylene					
Design	Bourdon tube pressure gauge					
Type of mounting	Can be screwed in					
Connection position	Centre, rear side					
Ambient temperature [°C]	-20 +60					
Accuracy of measurement, class	2.5					
Factor, continuous load	0.75					
Factor, intermittent load	0.66					
Protection class	IP43					
Materials	Housing: Acrylic butadiene styrene					
	Window shield: Polystyrene					
Weight [g]	62	76	88			

Indicating range							
Nominal size	40	50	63				
[bar]							
0 2.5	_						
0 10							
0 16							
[MPa]							
0 0.25	_	-					
0 1							
0 1.6							
[psi]							
0 36	-						
0 145							
0 232							

# Pressure gauge MA, DIN EN 837-1, with red-green range Technical data



Туре	D1	D2	L1	L2	L3
	Ø				
	±0.5		±1	±0.5	
MA-40E-RG	39	R <sup>1</sup> /8	46	28	10
MA-50E-RG	49	R <sup>1</sup> / <sub>4</sub>	49	28	13
MA-63E-RG	61.5	R1/4	50.5	29.5	13

Ordering data				
Nominal size	Pneumatic connection	Indicating range	Part No.	Туре
Display unit [bar	]			
40	R1/8	0 10	525 725	MA-40-10-R <sup>1</sup> /8-E-RG
		0 16	525 726	MA-40-16-R <sup>1</sup> /8-E-RG
50	R <sup>1</sup> / <sub>4</sub>	0 2.5	525 727	MA-50-2,5-R <sup>1</sup> / <sub>4</sub> -E-RG
		0 10	525 728	MA-50-10-R <sup>1</sup> / <sub>4</sub> -E-RG
		0 16	525 729	MA-50-16-R <sup>1</sup> / <sub>4</sub> -E-RG
63	R1/4	0 2.5	525 730	MA-63-2,5-R <sup>1</sup> / <sub>4</sub> -E-RG
		0 10	525 731	MA-63-10-R <sup>1</sup> / <sub>4</sub> -E-RG
		0 16	525 732	MA-63-16-R <sup>1</sup> / <sub>4</sub> -E-RG
Display unit [MP				
40	R <sup>1</sup> / <sub>8</sub>	0 1	526 778	MA-40-1,0-R <sup>1</sup> / <sub>8</sub> -MPA-E-RG
		0 1.6	526 779	MA-40-1,6-R <sup>1</sup> / <sub>8</sub> -MPA-E-RG
50	R <sup>1</sup> / <sub>4</sub>	0 0.25	526 780	MA-50-0,25-R <sup>1</sup> / <sub>4</sub> -MPA-E-RG
		0 1	526 781	MA-50-1,0-R <sup>1</sup> / <sub>4</sub> -MPA-E-RG
		0 1.6	526 782	MA-50-1,6-R <sup>1</sup> / <sub>4</sub> -MPA-E-RG
63	R <sup>1</sup> / <sub>4</sub>	0 0.25	526 783	MA-63-0,25-R <sup>1</sup> / <sub>4</sub> -MPA-E-RG
		0 1	526 784	MA-63-1,0-R <sup>1</sup> / <sub>4</sub> -MPA-E-RG
		0 1.6	526 785	MA-63-1,6-R <sup>1</sup> / <sub>4</sub> -MPA-E-RG
Display unit [psi]				
40	R <sup>1</sup> / <sub>8</sub>	0 145	526 786	MA-40-145-R <sup>1</sup> / <sub>8</sub> -PSI-E-RG
		0 232	526 787	MA-40-232-R <sup>1</sup> / <sub>8</sub> -PSI-E-RG
50	R <sup>1</sup> / <sub>4</sub>	036	526 788	MA-50-36-R <sup>1</sup> / <sub>4</sub> -PSI-E-RG
		0 145	526 789	MA-50-145-R <sup>1</sup> / <sub>4</sub> -PSI-E-RG
		0 232	526 790	MA-50-232-R <sup>1</sup> / <sub>4</sub> -PSI-E-RG
63	R <sup>1</sup> / <sub>4</sub>	0 36	526 791	MA-63-36-R <sup>1</sup> / <sub>4</sub> -PSI-E-RG
		0 145	526 792	MA-63-145-R <sup>1</sup> / <sub>4</sub> -PSI-E-RG
		0 232	526 793	MA-63-232-R <sup>1</sup> / <sub>4</sub> -PSI-E-RG



Function




- d - Temperature range −20 ... +60 °C




Technical data					
Nominal size	23	27	40	50	63
Pneumatic connection	R <sup>1</sup> /8	M5	G1/8	G <sup>1</sup> / <sub>4</sub>	G1/4
Operating medium	-	Liquid media			
	Gaseous media				
	Not permitted: Oxygen				
	Not permitted: Acetylen	e			
Design	Bourdon tube pressure	gauge			
Type of mounting	Can be screwed in				
Connection position	Centre, rear side				
Ambient temperature [°C]	-40 +60	0 +60	-20 +60		
Accuracy of measurement, class	_	4	2.5		
Factor, continuous load	-	0.75			
Factor, intermittent load	_	0.66			
Protection class	_	IP43			
For D series service units	-	MICRO	MINI	MIDI/MAXI	-
Materials	Housing:	Housing:	Housing: Acrylic butadie	ene styrene	
	Acrylic butadiene	Plastic			
	styrene				
	Sight glass:	Sight glass: Plastic	Sight glass: Polystyrene		
	Polystyrene				
	Threaded plug: Brass	Threaded plug: Brass	Threaded plug: Brass		
Weight [g]	16	11	70	70	70

Indicating range	9						
Nominal size		23	27	40	50	63	
[bar]	[psi]						
0 6	0 87		-	-	-	-	
0 10	0 145	•	-	•	•	-	
0 16	0 232	•	-	•	•	-	
0 20	0 290		-	_	_	_	
0 25	0 360		-	_	_		
[bar]							
0 10		-		-	_	_	
[MPa]							
0 0.6		-	-	-	-	-	
0 1		-				-	
0 1.6		-	-			_	
0 2.5		-	_			_	
	[psi]						
0 160		-		-	-	-	
			•	•	•	•	

Individual units Pressure gauges









Ordering data					
Nominal size	Pneumatic connection	Indicating range [bar]	[psi]	Part No. Type	
23	R <sup>1</sup> /8	0 6	0 87	183 896 MA-23-6	-R <sup>1</sup> / <sub>8</sub>
		0 10	0 145	183 897 MA-23-1	0-R <sup>1</sup> /8
		0 16	0 232	183 898 MA-23-1	6-R <sup>1</sup> /8
		0 20	0 290	537 916 MA-23-2	0-R½
	•	<u> </u>		·	
40	G1/8	0 10	0 145	359 874 MA-40-1	0-1/8
		0 16	0 232	345 395 MA-40-1	6-1/8
		·	·		
50	G <sup>1</sup> / <sub>4</sub>	0 10	0 145	359 873 MA-50-1	0-1/4
		0 16	0 232	356 759 MA-50-1	6-1/4
63	G1/4	0 25	0 360	7 169 MA-63-0	,25

Ordering data				
Nominal size	Pneumatic connection	Indicating range	Part No.	Туре
Display unit [bar	r]			
27	M5	0 10	526 323	MA-27-10-M5
Display unit [MP	a]			
27	M5	0 1	526 324	MA-27-1,0-M5-MPA
40	G1/4	0 0.6	184 285	MA-40-0,6-G <sup>1</sup> / <sub>4</sub> -MPA
		0 1	184 286	MA-40-1,0-G <sup>1</sup> / <sub>4</sub> -MPA
		0 1.6	184 287	MA-40-1,6-G <sup>1</sup> / <sub>4</sub> -MPA
		0 2.5	184 288	MA-40-2,5-G <sup>1</sup> / <sub>4</sub> -MPA
40	G1/8	0 1	192 732	MA-40-1-G <sup>1</sup> /8-MPA
		0 1.6	192 733	MA-40-1,6-G <sup>1</sup> /8-MPA
50	G1/4	0 1	192 734	MA-50-1-G <sup>1</sup> / <sub>4</sub> -MPA
		0 1.6	192 735	MA-50-1,6-G <sup>1</sup> / <sub>4</sub> -MPA
Display unit [psi	]			
27	M5	0 160	527 405	MA-27-160-M5-PSI

Individual units Pressure gauges

#### Function



- Temperature range -20 ... +60 °C



Technical data					
Nominal size	al size 40				
Pneumatic connection		R <sup>1</sup> / <sub>8</sub>			
Operating medium		Liquid media			
		Gaseous media			
		Not permitted: Oxygen			
		Not permitted: Acetylen	е		
Design		Bourdon tube pressure	gauge		
Indicating range	[bar]	0 1	0 4	0 6	0 16
	[psi]	0 14.5	0 58	0 87	0 232
Conforms to		DIN EN 837-1		<u> </u>	·
Type of mounting		Can be screwed in			
Connection position		Centre, rear side			
Ambient temperature	[°C]	-20 +60			
Accuracy of measurement, class	S	1.6			
Factor, continuous load		0.75			
Factor, intermittent load		0.66			
Protection class		IP43			
Materials		Housing: Acrylic butadio	ene styrene		
		Sight glass: Polystyrene		<u> </u>	
		Threaded plug: Brass			
Weight	[g]	60			



Ordering data	Ordering data						
Nominal size	Pneumatic	Indicating range		Part No.	Туре		
	connection	[bar]	[psi]				
40	R <sup>1</sup> /8	0 1	0 14.5	161 126	MAP-40-1-1/8-EN		
		0 4	0 58	162 842	MAP-40-4-1/8-EN		
		0 6	0 87	161 127	MAP-40-6-1/8-EN		
		0 16	0 232	161 128	MAP-40-16-1/8-EN		

Core Range



Function







Technical data	Fechnical data					
Nominal size		15				
Pneumatic connection		QS4	QS6	QS8		
Operating medium		Filtered compressed air, lubricated or u	nlubricated			
Design		Bourdon tube pressure gauge without r	neasuring mechanism			
Indicating range	[bar]	0 10				
Type of mounting		Can be screwed in				
Connection position		Centre, rear side				
Ambient temperature	[°C]	0 +60				
Factor, continuous load		0.75				
Materials		Housing: Nickel plated steel				
Weight	[g]	8	10	13		



Dimensions and ordering data							
Nominal size	Indicating range	Pneumatic	L	L1	L2	Part No.	Туре
D	[bar]	connection					
15	0 10	QS4	36	23	15	153 383	MA-15-10-QS-4
		QS6	38	25	17	153 384	MA-15-10-QS-6
		QS8	34	21	18.5	153 385	MA-15-10-QS-8

# Flanged pressure gauge FMA, DIN EN 837-1 Technical data

**FESTO** 

Function








Technical data				
Nominal size	40	50	63	
Pneumatic connection	G1/4			
Operating medium	Liquid media			
	Gaseous media			
	Not permitted: Oxygen			
	Not permitted: Acetylene			
Design	Bourdon tube pressure gauge			
Conforms to	DIN EN 837-1			
Type of mounting	Panel mounting			
Connection position	Centre, rear side			
Ambient temperature [°C]	-20 +60			
Accuracy of measurement, class	2.5			
Factor, continuous load	0.75			
Factor, intermittent load	0.66			
Protection class	IP43			
Materials	Housing: Polystyrene			
	Sight glass: Styrene acrylonitrile copolymer Threaded plug: Brass			
Weight [g]	80	100	120	

Indicating range							
[bar]	[psi]	Nominal size					
		40 50 63					
0 2.5	0 36	-		•			
0 10	0 145						
0 16	0 232						



Туре	B1	B2	D1 Ø	D2 Ø	L1	L2	L3
FMA-40	48	56	40	45	4.5	26.5	43
FMA-50	57	66	49.5	54	4.5	26.8	43.3
FMA-63	70	79	63	68	4.8	29.5	42.5

Ordering data						
Nominal size	Pneumatic	Indicating range		Part No.	Туре	
	connection	[bar]	[psi]			
40	G1/4	0 10	0 145	159 596	FMA-40-10-1/4-EN	
		0 16	0 232	159 597	FMA-40-16-1/4-EN	
50	50	G1/4	0 2.5	0 36	159 598	FMA-50-2,5-1/4-EN
		0 10	0 145	159 599	FMA-50-10-1/4-EN	
		0 16	0 232	159 600	FMA-50-16-1/4-EN	
63	63	G1/4	0 2.5	0 36	159 601	FMA-63-2,5-1/4-EN
			0 10	0 145	159 602	FMA-63-10-1/4-EN
		0 16	0 232	159 603	FMA-63-16-1/4-EN	

**FESTO** 


Function







Technical data		
Nominal size		63
Pneumatic connection		G1/ <sub>4</sub>
Operating medium		Gaseous media
Design		Aneroid pressure gauge
Indicating range	[bar]	0 0.25
Indicating range	[psi]	0 3.6
Type of mounting		Panel mounting
Connection position		Centre, rear side
Ambient temperature	[°C]	-10 +60
Accuracy of measurement, class		2.5
Factor, continuous load		0.75
Factor, intermittent load		0.66
Protection class		IP43
Materials		Housing: Steel
		Sight glass: Polymethylmethacrylate
		Threaded plug: Brass
Weight	[g]	240




Ordering data								
Nominal size	Pneumatic	Indicating range			Туре			
	connection	[bar]	[psi]					
63	G1/4	0 0.25	0 3.6	225 783	FMA-63-0,25-C			







Technical data							
Nominal size		63					
Pneumatic connection		G1/4					
Operating medium		Liquid media					
		Gaseous media					
		Not permitted: Oxygen					
		Not permitted: Acetylene					
Design		Bourdon tube pressure gauge					
Indicating range	[bar]	0 1	0 4	0 6	0 16		
	[psi]	0 14.5	0 58	0 87	0 232		
Conforms to		DIN EN 837-1					
Type of mounting		Panel mounting					
Connection position		Centre, rear side					
Ambient temperature [°C]		-20 +60					
Accuracy of measurement, class	S	1.0					
Factor, continuous load		0.75					
Factor, intermittent load		0.66					
Protection class		IP43					
Materials		Housing: Polystyrene					
		Sight glass: Styrene acrylonitrile copolymer					
Threaded plug: Brass							
Weight	[g]	120					



Ordering data								
Nominal size	Pneumatic	Indicating range			Туре			
	connection	[bar]	[psi]					
63	G1/4	0 1	0 14.5	161 129	FMAP-63-1- <sup>1</sup> / <sub>4</sub> -EN			
		0 4	0 58	162 843	FMAP-63-4-1/4-EN			
		0 6	0 87	161 130	FMAP-63-6-1/4-EN			
		0 16	0 232	161 131	FMAP-63-16-1/4-EN			

### **Product Range and Company Overview**

#### **A Complete Suite of Automation Services**

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



**Custom Automation Components**Complete custom engineered solutions



**Custom Control Cabinets**Comprehensive engineering support and on-site services



**Complete Systems**Shipment, stocking and storage services

#### **The Broadest Range of Automation Components**

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



**Electromechanical**Electromechanical actuators, motors, controllers & drives



**Pneumatics**Pneumatic linear and rotary actuators, valves, and air supply



PLC's and I/O Devices
PLC's, operator interfaces, sensors
and I/O devices

#### Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

#### Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



#### **Festo North America**

#### **United States**

#### **Customer Resource Center**

502 Earth City Expy., Suite 125 Earth City, MO 63045

For ordering assistance, or to find your nearest Festo Distributor, **Call:** 1.800.99.FESTO **Fax:** 1.800.96.FESTO

Email: customer.service@us.festo.com

For technical support,
Call: 1.866.GO.FESTO
Fax: 1.800.96.FESTO

Email: product.support@us.festo.com

#### Headquarters

Festo Corporation 395 Moreland Road P.O. Box 18023 Hauppauge, NY 11788 www.festo.com/us

#### **Sales Offices**

#### Appleton

N. 922 Tower View Drive, Suite N Greenville, WI 54942

#### **Boston**

120 Presidential Way, Suite 330 Woburn, MA 01801

#### Chicago

1441 East Business Center Drive Mt. Prospect, IL 60056

#### **Dallas**

1825 Lakeway Drive, Suite 600 Lewisville, TX 75057

**Detroit** - Automotive Engineering Center 2601 Cambridge Court, Suite 320 Auburn Hills, MI 48326

#### New York

395 Moreland Road Hauppauge, NY 11788

#### Silicon Valley

4935 Southfront Road, Suite F Livermore, CA 94550

#### **Design and Manufacturing Operations**



East: 395 Moreland Road, Hauppauge, NY 11788



Central: 1441 East Business Center Drive, Mt. Prospect, IL 60056



West: 4935 Southfront Road, Suite F, Livermore, CA 94550

#### Mexico

#### Headquarters

Festo Pneumatic, S.A.

Av. Ceylán 3, Col. Tequesquinahuac
54020 Tlalnepantla, Edo. de México
Call: 011 52 [55] 53 21 66 00

Fax: 011 52 [55] 53 21 66 65

Email: festo.mexico@mx.festo.com

www.festo.com/mx



#### Canada

#### Headquarters

Festo Inc. 5300 Explorer Drive

Mississauga, Ontario L4W 5G4

Call: 1.905.624.9000 Fax: 1.905.624.9001 Email: info.ca@ca.festo.com

www.festo.com/ca



#### **Festo Worldwide**

Argentina Australia Australia Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela