


Vacuum generators VADM/VADMI

FESTO




Vacuum generators

Key features

FESTO

Product overview

Vacuum generator



All Festo vacuum generators have a single-stage design and operate according to the venturi principle. The product families described below

have been designed for a wide range of applications. The different performance classes of the individual

product families make it possible to select vacuum generators tailored to suit specific requirements.

Standard and inline ejectors

VN-...

Technical data → Internet: vn



- Nominal size 0.45 ... 3 mm
- Max. vacuum 93%
- Temperature range 0 ... +60 °C
- A range of extremely effective generators suitable for use directly in the workplace
- Available as straight or T-shaped housing
- Low space requirement
- Low-cost
- No wearing parts
- Extremely fast evacuation time
- Vacuum switch (optional)
- Optional with additional functions:
 - integrated eject pulse
 - electric control for vacuum ON/OFF
 - combination of eject pulse and control

VAD-.../VAK-...

Technical data → Internet: vad



- Nominal size 0.5 ... 1.5 mm
- Max. vacuum 80%
- Temperature range -20 ... +80 °C
- Range of vacuum generators with sturdy aluminium casing
- VAK-...: Built-in reservoir
- VAD-...: Connection for additional external reservoir
- Maintenance-free
- VAK-...: Reliable setting down of workpieces

Vacuum generators

Key features

FESTO

Compact ejectors

VADM-.../VADMI-...

→ 8



- Nominal size
0.45 ... 3 mm
- Max. vacuum
84%
- Temperature range
0 ... +60 °C
- Compact design
- Minimal installation work required
- Short response times
- Built-in solenoid valve (on/off)
- VADMI-...: Additional built-in solenoid valve for ejector pulse
- Filter with display
- Air-saving function (optional)
- Vacuum switch (optional)
- Reliable setting down of workpieces

VAD-M-.../VAD-M-I-...

Technical data → Internet: vad-m



- Nominal size
0.7 ... 2 mm
- Max. vacuum
85%
- Temperature range
0 ... +40 °C
- Compact design
- Minimal installation work required
- Short response times
- Built-in solenoid valve (on/off)
- VAD-M-I-...: Additional built-in solenoid valve for ejector pulse
- Reliable setting down of workpieces

Vacuum generators VADM/VADMI

FESTO

Features

At a glance

- Compact and sturdy design
- Components with numerous individual functions form a single unit
- Extremely short switching times thanks to integrated solenoid valves
- No external or additional components required
- Easily fitted thanks to compact dimensions and therefore particularly suitable for handling operations
- Cost effective assembly as the solenoid valve, vacuum generator and silencer are all in a single unit.
- Protection class IP65
- With manual override
- With integrated silencer for reducing exhaust noise
- With integrated filter for the air to be evacuated and a display window which shows the degree of filter contamination
- With or without integrated vacuum switch to monitor the vacuum with PNP or NPN output
- With 2 vacuum ports, optional

Vacuum generator VADM-.../-...-P/-N

The compressed air supply of these vacuum generators is controlled by the built-in solenoid valve.


When the electrical power supply is switched on, the valve is actuated and the flow of compressed air from 1 (P) to 3 (R) generates a vacuum at port 2 (V), operating on the ejector principle. Suction stops when the supply power to the valve is switched off.

The integrated silencer reduces exhaust noise to a minimum.

- Built-in solenoid valve for:
 - Vacuum ON/OFF


With the vacuum generators VADM-...-P/N the vacuum can be monitored by means of a vacuum switch.

VADM-...



VADM-...-P/-N

with vacuum switch



1 = Pressure supply port
2 = Vacuum port



Vacuum generator VADMI-.../-...-P/-N with ejector pulse and vacuum switch

Compressed air enters the vacuum generator following the application of a voltage signal to the integrated solenoid valve, thereby creating a vacuum.

Once the voltage is switched off at the vacuum valve and switched on at the ejector valve, the vacuum is rapidly purged at port 2 as a result of the application of pressure.


The integrated silencer reduces exhaust noise to a minimum.

- Two built-in solenoid valves for:
 - Vacuum ON/OFF
 - Ejector pulse
- With sensing interface
- With integrated non-return valve as safety function

With the vacuum generators VADMI-...-P/-N the vacuum can be monitored by means of a vacuum switch.


VADMI-...

with ejector pulse



VADMI-...-P/-N

with ejector pulse and vacuum switch



1 = Pressure supply port
2 = Vacuum port



Vacuum generators VADM/VADMI

Features

FESTO


Vacuum generator VADMI-...-LS-P/N with ejector pulse, vacuum switch and air-saving function

This vacuum generator is identically constructed to the other VADMI types. In addition, however, this ejector has a built-in vacuum switch with air-saving function:

If the vacuum level falls below the required range, vacuum generation is activated automatically (operating principle of vacuum switch for VADMI-...-LS-P/N → 13).

- Solenoid valve for vacuum generation
- Integrated silencer
- Integrated 40 µm filter with contamination indication
- With sensing interface for vacuum fault signal
- With integrated non-return valve as safety function
- With vacuum switch for pressure monitoring
- With 2 vacuum ports

VADM-...-LS-P/N
with air-saving function
PNP output



1 = Pressure supply port
2 = Vacuum port





Vacuum generators VADM/VADMI

Peripherals overview

FESTO

VADM/VADMI-45/70

VADM/VADMI-95/140/200/300




| Mounting attachments and accessories | | | |
|--------------------------------------|------------------|---------------------------|-----------------|
| | VADM/VADMI-45/70 | VADM/VADMI-95/140/200/300 | → Page/Internet |
| 1 Push-in fitting QS | ■ | ■ | quick star |
| 2 Suction gripper ESG | ■ | ■ | esg |
| 3 Connecting cable NEBU-M8 | ■ | ■ | nebu-m8 |
| 4 Connecting cable KMYZ-2 | ■ | - | kmyz-2 |
| 5 Plug socket with cable KMYZ-4 | ■ | - | kmyz-4 |
| 6 Plug socket with cable KMEB-1/2 | - | ■ | kmeb |
| 7 Plug socket MSSD-ZBZC | ■ | - | mssd-zbzc |
| 8 Plug socket MSSD-EB | - | ■ | mssd-eb |
| - Suction cup holder ESH | ■ | ■ | esh |
| - Suction cup ESS | ■ | ■ | ess |
| - Illuminating seal MEB-LD | - | ■ | meb-ld |

Vacuum generators VADM/VADMI

Type codes



| | | | | | | | | |
|---------------------------------------|--|------|---|----|---|----|---|---|
| | | VADM | — | 45 | — | LS | — | P |
| Type | | | | | | | | |
| VADM | Vacuum generator without ejector pulse | | | | | | | |
| VADMI | Vacuum generator with ejector pulse | | | | | | | |
| Nominal laval nozzle size [mm] | | | | | | | | |
| 45 | 0.45 | | | | | | | |
| 70 | 0.70 | | | | | | | |
| 95 | 0.95 | | | | | | | |
| 140 | 1.40 | | | | | | | |
| 200 | 2.00 | | | | | | | |
| 300 | 3.00 | | | | | | | |
| Functions | | | | | | | | |
| LS | With air-saving function | | | | | | | |
| Switching type | | | | | | | | |
| P | PNP design (vacuum switch, output potential) | | | | | | | |
| N | NPN design (vacuum switch, output potential) | | | | | | | |

 Note
Possible combinations can be found in the ordering data.


Vacuum generators VADM/VADMI


Technical data


FESTO


Function

VADM-...




-  - Temperature range
-0 ... +60 °C


-  - Operating pressure
1.5 ... 8 bar



VADMI-...



| General technical data | | | | | | |
|-----------------------------------|--|---------|-------------|-----------|-----------|-----------|
| Nominal size | 45 | 70 | 95 | 140 | 200 | 300 |
| Design | Slim rectangular | | | | | |
| Mounting position | Any | | | | | |
| Ejector features | High vacuum | | | | | |
| Type of mounting | Either: Via female thread, via through-holes | | | | | |
| Pneumatic connection 1/2 | M5/M5 | M5/G1⁄8 | G1⁄8/G1⁄8 | G1⁄8/G1⁄4 | G1⁄4/G3⁄8 | G1⁄4/G3⁄8 |
| Nominal size of laval nozzle [mm] | 0.45 | 0.7 | 0.95 | 1.4 | 2.0 | 3.0 |
| Duty cycle [%] | 100 | | | | | |
| Power consumption [W] | 1.4 | | 1.5 piloted | | | |
| Protection class | IP65 | | | | | |

-  - Note: This product conforms to ISO 1179-1 and to ISO 228-1

| Operating and environmental conditions | | | | | | |
|--|---|----|---------|-----|-----|-----|
| Nominal size | 45 | 70 | 95 | 140 | 200 | 300 |
| Operating pressure [bar] | 1.5 ... 8 | | 2 ... 8 | | | |
| Operating medium | Compressed air in accordance with ISO 8573-1:2010 [7:4:4] | | | | | |
| Note on operating/pilot medium | Operation with lubricated medium not possible | | | | | |
| Ambient temperature [°C] | 0 ... +60 | | | | | |
| Corrosion resistance class CRC ¹⁾ | 2 | | | | | |
| Note on materials | Free of copper and PTFE | | | | | |
| Certification | c UL us - Recognized (OL) | | | | | |

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.


| Weights [g] | | | | | | |
|----------------------|----|-----|-----|-----|-----|-----|
| Nominal size | 45 | 70 | 95 | 140 | 200 | 300 |
| VADM-... | 60 | 140 | 210 | 290 | 320 | 340 |
| VADM-...-P/-N | 65 | 145 | 220 | 300 | 330 | 350 |
| VADMI-... | 85 | 170 | 240 | 320 | 350 | 370 |
| VADMI-...-P/-N/-LS-P | 90 | 180 | 250 | 330 | 360 | 380 |

Vacuum generators VADM/VADMI




Technical data

FESTO

Vacuum Δp_u as a function of operating pressure p



Evacuation time t [s] for 1 litre volume at 6 bar operating pressure



Air supply time for 1 litre volume at 6 bar operating pressure¹⁾

| Type | With ejector pulse [s] | Without ejector pulse [s] | Max. flow rate [l/min] |
|---------------|---------------------------|------------------------------|---------------------------|
| VADM-45-... | – | 5.9 | – |
| VADMI-45-... | 1.9 | – | 21 |
| VADM-70-... | – | 2.2 | – |
| VADMI-70-... | 0.59 | – | 48 |
| VADM-95-... | – | 1.18 | – |
| VADMI-95-... | 0.24 | – | 104 |
| VADM-140-... | – | 0.69 | – |
| VADMI-140-... | 0.19 | – | 265 |
| VADM-200-... | – | 0.29 | – |
| VADMI-200-... | 0.15 | – | 260 |
| VADM-300-... | – | 0.26 | – |
| VADMI-300-... | 0.2 | – | 250 |



1) Time required to build up vacuum from -0.75 to -0.05 bar.

Vacuum generators VADM/VADMI


Technical data

FESTO


Air consumption Q as a function of operating pressure p




Noise level Lp as a function of operating pressure p (without suction flow)



Efficiency η as a function of vacuum Δp_u at P_{nom} 6 bar



Suction rate qn as a function of vacuum Δp_u





Vacuum generators VADM/VADMI

Technical data


FESTO

Vacuum switch for vacuum generators
VADM...-...-P/N

Circuit diagram



- Piezo-resistive vacuum switch with adjustable switching point and adjustable hysteresis
- Switching status display, yellow LED
- Electrical connection, polarity safe



General technical data

Pneumatic data

| | | |
|-------------------------|-------|------------------------------------|
| Max. operating pressure | [bar] | 0 ... -0.95 |
| Switching point | [bar] | 0 ... -0.9 (adjustable) |
| Hysteresis | [bar] | 0.05 ... 0.5 (adjustable) |
| Temperature influence | | ≤ ±5 mbar/10K (on switching point) |

Electrical data

| | | |
|------------------------------------|--------|----------------------------|
| Operating voltage | [V DC] | 24 (15 ... 30) |
| Voltage drop | [V] | 1.2 (at switch output) |
| Switch output current | [mA] | 130 |
| Max. intrinsic current consumption | [mA] | 25 |
| Max. switching delay | [ms] | 5 |
| Connection | | Reverse polarity protected |

Mechanical data

| | |
|--------|--|
| Design | Piezo-resistive vacuum switch with adjustable switching point and hysteresis |
|--------|--|

Ambient conditions

| | |
|------------------|------|
| Protection class | IP65 |
|------------------|------|


Operating and environmental conditions

| | | |
|---|------|-----------------------------------|
| Ambient temperature | [°C] | 0 ... +60 |
| Note on materials | | Free of copper and PTFE |
| CE mark (see declaration of conformity) | | To EU EMC Directive ¹⁾ |
| Certification | | c UL us - Recognized (OL) |
| | | RCM Mark |

1) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com/sp → Certificates.

If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

Vacuum switch control panel



- 1 Switching status display, yellow LED
- 2 Switching point adjustment
- 3 Hysteresis adjustment


Vacuum generators VADM/VADMI

Technical data


FESTO

Terminal allocation

PNP output




NPN output



BN = Brown
WH = White
BK = Black
BU = Blue
RL = Load

Pin allocation



1 Brown: Positive terminal
2 White: NC contact
3 Blue: Negative terminal
4 Black: NO contact

Energy-saving function with VADMI...-P/N

The conventional vacuum switch → A cost-effective energy-saving measure


With the vacuum generators VADMI a maximum value is first set and then the hysteresis is regulated (reliable operating range). The lower limit defines the minimum value.

Once the vacuum level is within this range, reliable workpiece transport is guaranteed.


The vacuum generator VADMI is only activated by the external controller if the level drops below the minimum value and is deactivated again once that minimum value is regained.

A non-return valve prevents the vacuum level from being purged during the inactive phase of vacuum generation.

The functional sequence



Optimum vacuum curve
Actual vacuum curve



RP Ejector pulse
VG Vacuum on/off
E Vacuum generator
D Non-return valve
A Vacuum switch

Vacuum on

- 1 External controller F switches on the VG solenoid
 - Valve for compressed air supply B is opened
 - Vacuum generation E is activated

Vacuum stop

- 2 The specified maximum level is achieved:
 - Pressure sensor A sends a signal to the external controller
 - Controller switches the VG solenoid off
 - Vacuum generation is interrupted
 - Non-return valve D prevents the vacuum level from being purged

Vacuum on

- 3 Leakage causes the vacuum level to drop to the minimum value
 - Pressure sensor A sends a signal to the external controller F
 - Controller F switches the VG solenoid B back on
 - Vacuum generation E is active again
 - Constant repetition of points 2 and 3

Cycle ended: Vacuum off

- 4 Transport process ended
 - External controller (PLC) F deactivates VG solenoid B
 - Vacuum generation E is ended
 - External controller switches on ejector RP solenoid C
 - Vacuum level at 0
 - Workpiece is released



Vacuum generators VADM/VADMI

Technical data

FESTO

Vacuum switch and cable set for vacuum generators with air-saving function VADMI-...-LS-P/N

Circuit diagram



- Piezo-resistive vacuum switch with adjustable switching point and adjustable hysteresis
- Air-saving function only in conjunction with supplied cable
- Switching status display, yellow LED
- Electrical connection, polarity safe



| General technical data | | |
|------------------------------------|--------|---|
| Pneumatic data | | |
| Max. operating pressure | [bar] | 0 ... 1 |
| Max. overload pressure | [bar] | 5 (for t < 1 min) |
| Switching point | [bar] | 0 ... -0.9 (adjustable) |
| Hysteresis | [bar] | 0.1 ... 0.6 (adjustable) |
| Temperature influence | | ≤ ±10 mbar/10K (on switching point) |
| Electrical data | | |
| Operating voltage | [V DC] | 24 V (±10%, at VADMI-70-LS-P +10%–5%) |
| Voltage drop | [V] | 1.2 (at switch output) |
| Switch output current | [mA] | 130 |
| Max. intrinsic current consumption | [mA] | 25 |
| Max. switching delay | [ms] | 2 (with NPN cable distribution: 20 ms) |
| Connection | | Reverse polarity protected |
| Mechanical data | | |
| Design | | Piezo-resistive vacuum switch with integrated air-saving function |
| Ambient conditions | | |
| Protection class | | IP65 |

| Operating and environmental conditions | | |
|---|------|-----------------------------------|
| Ambient temperature | [°C] | 0 ... +60 |
| Note on materials | | Free of copper and PTFE |
| CE mark (see declaration of conformity) | | To EU EMC Directive ¹⁾ |
| Certification | | c UL us - Recognized (OL) |
| | | RCM Mark |

1) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com/sp → Certificates.
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

Vacuum generators VADM/VADMI

Technical data

FESTO

Function principle

In conjunction with the supplied cable set, the vacuum generator VADMI-...-LS-P/N contains an air-saving function. The vacuum range to be used to hold the workpiece is set on the switch using both potentiometers.

The switch generates a pulsating signal A2 which only actuates the solenoid for vacuum ON/OFF in the vacuum generator when the vacuum pressure has fallen below the selected upper limit value due to leakage etc.


At all other times, the vacuum is maintained with the help of the non-return valve, even when the vacuum generator is not switched on. In addition to this, status signal A1 can be interrogated which is connected to +24 V during normal operation, but which is switched to 0 whenever vacuum pressure falls below the critical value by 150 mbar due to a malfunction.

This is the case, for example, if the workpiece has dropped off from the suction cup and it is no longer possible to generate the selected vacuum.

Accessories (included in scope of delivery):

- Connecting cable
The switch may only be operated with the included cable set.
Connections 1, 2 and 4 can nevertheless be interchanged with one another without damaging the device.


Vacuum switch control panel




- 1 Switching status display, yellow LED
- 2 Switching point adjustment
- 3 Hysteresis adjustment

Terminal allocation

PNP output




NPN output




BN = Brown
WH = White
BK = Black
BU = Blue
RL = Load

Pin allocation



- 1 Brown: Positive terminal
- 2 White: NC contact
- 3 Blue: Negative terminal
- 4 Black: NO contact

Switching points/hysteresis



Vacuum generators VADM/VADMI

Technical data

FESTO

Energy-saving function and error reporting with VADMI-...-LS-P/N



The further development of the vacuum switch

In addition to the described functions, error reporting is also used as an additional energy-saving measure. This like the vacuum circuit is controlled via the vacuum switch.

If a suction cup does not pick up a workpiece properly or a tube bursts, the vacuum switch can report such an event to the external control unit (PLC) F so that this or the user can take the necessary steps.

Given the decentrally controlled switching function, external actuation of the vacuum circuit (air-saving function) would be superfluous. As a result there is significantly less wiring.

The functional sequence



Start signal

- 1 External controller F activates the pressure sensor
→ Pressure sensor A checks the vacuum status
→ No vacuum present

Vacuum on

- 2 Pressure sensor activates the VG solenoid B
→ Valve for compressed air supply is opened
→ Vacuum generation E is activated
- 3 Vacuum level 150 mbar below the maximum level is exceeded
→ Pressure sensor sends an enable signal to external controller (PLC) F BK
→ Transport process can start

Vacuum stop

- 4 The specified maximum level is achieved
→ Pressure sensor A switches the VG solenoid off
→ Compressed air supply stopped
→ Vacuum generation E interrupted
→ Non-return valve D prevents the vacuum level from being purged

Vacuum on

- 5 Leakage causes the vacuum level to drop to the minimum value
→ Pressure sensor A switches the VG solenoid on again
→ Vacuum generation E is active again

Fault: Transport stopped

- 6 Major leakage causes an overly large drop in the vacuum level
→ Vacuum generator E cannot compensate for the drop in level
- 7 Vacuum level is 150 mbar below the minimum value
→ Pressure sensor A sends an error message to the external controller (PLC) F BK
→ External controller interrupts the transport process
→ Vacuum generation E is ended

Cycle ended: Vacuum off

- 8 Transport process ended
→ External controller (PLC) F deactivates VG solenoid
→ Vacuum generation E is ended
→ External controller F switches on ejector RP solenoid C WH
→ Ejector pulse activated
→ Workpiece is released

Vacuum generators VADM/VADMI

Technical data

FESTO

Connection to PLC

PNP and NPN switching of the VADMI-...-LS-P/N

The three control and supply cable harnesses are combined in a branching directly via the vacuum generator so that only one cable containing one signal wire and three

voltage supply wires need to be conducted from the branching to the PLC.
In principle there are two different signal characteristics with external control units (PLC) for the vacuum generator VADMI-LS, which differ only

slightly in their mode of operation. As both versions are identical in terms of the vacuum generator and the vacuum switch, the signal flow is only converted in the branching, as this is the only difference between the models.

The labelled plug-in connectors for the wiring harness are connected to the relevant elements of the VADMI-LS. The four-wire cable splice of the branching is connected to the control unit in the manner depicted below.

VADMI-...



VADMI
without vacuum circuit

VADMI-...-P/N



VADMI
with vacuum switching

VADMI-...-P/N-LS




VADMI
with air-saving function

four-wire cable splice




PNP circuit



BN = Brown for vacuum generation VG
WH = White for ejector pulse RP

BK = Black for consumer R_L (PLC)
BU = Blue for ground

NPN circuit



Vacuum generators VADM/VADMI


Technical data

FESTO

Dimensions

VADM-45/-70

VADM-95/-140/-200/-300



- 1 Compressed air port
- 2 Vacuum port
- 3 Manual override facility
- 4 Mounting thread
- 5 Mounting hole
- 6 Solenoid coil can be repositioned by 180°
- 7 Suitable socket for:
VADM-45/-70
KMYZ-...
→ Internet: kmyz
VADM-95/-.../-300
KMEB-... and MSSD-EB
→ Internet: kmeb1
→ Internet: mssd-eb

| Type | B1 | B2 | B3 | D1 | D2 | D3 Ø | D4 | H1 | H2 | H3 | H4 | H5 | H6 | H7 |
|----------|----|------|----|------|------|---------|------|-------|------|------|------|------|------|------|
| VADM-45 | 10 | 6.2 | – | M5 | M5 | 3.2 | M2 | 64.4 | 44.4 | 40.8 | 23.8 | 23.8 | 29.6 | 18 |
| VADM-70 | 15 | 11.2 | – | G1/8 | M5 | 3.2 | M2 | 73.9 | 49.4 | 47 | 26.5 | 23.5 | 32.9 | 18 |
| VADM-95 | 18 | 13.4 | 18 | G1/8 | G1/8 | 4.2 | M2.5 | 93.4 | 63.4 | 48.9 | 25.5 | 23.3 | 33 | 18 |
| VADM-140 | 22 | 16.6 | 18 | G1/4 | G1/8 | 5.2 | M3 | 107.4 | 77.4 | 61.4 | 41.4 | 41.4 | 36 | 17.5 |
| VADM-200 | 22 | 16.6 | 18 | G3/8 | G1/4 | 5.2 | M3 | 113.4 | 83.4 | 67.7 | 41.4 | 41.4 | 40 | 19 |
| VADM-300 | 22 | 16.6 | 18 | G3/8 | G1/4 | 5.2 | M3 | 113.4 | 83.4 | 67.7 | 41.4 | 41.4 | 40 | 19 |

| Type | L1 | L2 | L4 | L5 | L6 | L7 | L8 | L9 | L10 | L11 | L12 | L13 | L14 |
|----------|-------|-------|------|------|------|-----|------|------|-------|------|-----|-------|-----|
| VADM-45 | 45 | 41 | 33.6 | 25 | 3.6 | 11 | 16 | 41 | 56 | 7.9 | 1.9 | 36.3 | 4 |
| VADM-70 | 62.3 | 58.3 | 40.4 | 21 | 14.2 | 11 | 22 | 52.4 | 76.1 | 9.4 | 1.9 | 53.7 | 4.5 |
| VADM-95 | 65 | 61 | 43.3 | 8.7 | 13.2 | 9.7 | 24.5 | 61 | 78.8 | 9.5 | 2.3 | 55 | 4.5 |
| VADM-140 | 88 | 84 | 26 | 12.5 | 28.5 | 9.7 | 24.5 | 61 | 96.8 | 13.8 | 2.3 | 79.4 | 5 |
| VADM-200 | 88 | 84 | 26 | 12.5 | 28.5 | 9.7 | 24.5 | 61 | 101.8 | 12.5 | 2.3 | 79.4 | 5 |
| VADM-300 | 124.4 | 120.4 | 26 | 12.5 | 28.5 | 9.7 | 24.5 | 61 | 137.4 | 12.5 | 2.3 | 115.8 | 5 |

– Note: This product conforms to ISO 1179-1 and to ISO 228-1

Vacuum generators VADM/VADMI


Technical data

FESTO

Dimensions

VADM-45/-70-P/-N

VADM-95/-140/-200/-300-P/-N



| Type | B1 | B2 | B3 | D1 | D2 | D3 Ø | D4 | H1 | H2 | H3 | H4 | H5 | H6 | H7 |
|---------------|----|------|----|------|------|---------|------|-------|------|------|------|------|------|------|
| VADM-45-P/-N | 10 | 6.2 | 10 | M5 | M5 | 3.2 | M2 | 64.4 | 44.4 | 40.8 | 23.8 | 23.8 | 29.6 | 18 |
| VADM-70-P/-N | 15 | 11.2 | 15 | G1/8 | M5 | 3.2 | M2 | 73.9 | 49.4 | 47 | 26.5 | 23.5 | 32.9 | 18 |
| VADM-95-P/-N | 18 | 13.4 | 18 | G1/8 | G1/8 | 4.2 | M2.5 | 93.4 | 63.4 | 48.9 | 25.5 | 23.3 | 33 | 18 |
| VADM-140-P/-N | 22 | 16.6 | 18 | G1/4 | G1/8 | 5.2 | M3 | 107.4 | 77.4 | 61.4 | 41.4 | 41.4 | 36 | 17.5 |
| VADM-200-P/-N | 22 | 16.6 | 18 | G3/8 | G1/4 | 5.2 | M3 | 113.4 | 83.4 | 67.7 | 41.4 | 41.4 | 40 | 19 |
| VADM-300-P/-N | 22 | 16.6 | 18 | G3/8 | G1/4 | 5.2 | M3 | 113.4 | 83.4 | 67.7 | 41.4 | 41.4 | 40 | 19 |

| Type | L1 | L2 | L3 | L4 | L5 | L6 | L7 | L8 | L9 | L10 | L11 | L12 | L13 | L14 |
|---------------|-------|-------|------|------|------|------|-----|------|------|-------|------|-----|-------|-----|
| VADM-45-P/-N | 71.4 | 41 | 28.4 | 33.6 | 25 | 3.6 | 11 | 16 | 41 | 56 | 7.9 | 1.9 | 36.3 | 4 |
| VADM-70-P/-N | 88.7 | 58.3 | 28.4 | 40.4 | 21 | 14.2 | 11 | 22 | 52.4 | 76.1 | 9.4 | 1.9 | 53.7 | 4.5 |
| VADM-95-P/-N | 91.4 | 61 | 28.4 | 43.3 | 8.7 | 13.2 | 9.7 | 24.5 | 61 | 78.8 | 9.5 | 2.3 | 55 | 4.5 |
| VADM-140-P/-N | 114.4 | 84 | 28.4 | 26 | 12.5 | 28.5 | 9.7 | 24.5 | 61 | 96.8 | 13.8 | 2.3 | 79.4 | 5 |
| VADM-200-P/-N | 114.4 | 84 | 28.4 | 26 | 12.5 | 28.5 | 9.7 | 24.5 | 61 | 101.8 | 12.5 | 2.3 | 79.4 | 5 |
| VADM-300-P/-N | 150.8 | 120.4 | 28.4 | 26 | 12.5 | 28.5 | 9.7 | 24.5 | 61 | 137.4 | 12.5 | 2.3 | 115.8 | 5 |

- || - Note: This product conforms to ISO 1179-1 and to ISO 228-1

Vacuum generators VADM/VADMI


Technical data

FESTO

Dimensions

VADMI-45/-70

VADMI-95/-140/-200/-300



- 1 Compressed air port
- 2 Vacuum port
- 3 Manual override facility
- 4 Mounting thread
- 5 Mounting hole
- 7 Suitable socket for:
 VADMI-45/-70
 KMYZ-...
 → Internet: kmyz
 VADMI-95/-.../-300
 KMEB-... and MSSD-EB
 → Internet: kmeb1
 → Internet: mssd-eb

| Type | B1 | B2 | B3 | D1 | D2 | D3 Ø | D4 | H1 | H2 | H3 | H4 | H5 | H6 | H7 |
|-----------|----|------|----|------|------|---------|------|-------|------|------|------|------|------|------|
| VADMI-45 | 10 | 6.2 | – | M5 | M5 | 3.2 | M2 | 78.2 | 58.2 | 40.8 | 23.8 | 23.8 | 43.4 | 18 |
| VADMI-70 | 15 | 11.2 | – | G1/8 | M5 | 3.2 | M2 | 88.9 | 64.4 | 47 | 26.5 | 23.5 | 48.8 | 18 |
| VADMI-95 | 18 | 13.4 | 18 | G1/8 | G1/8 | 4.2 | M2.5 | 99.4 | 69.4 | 48.9 | 25.5 | 23.3 | 33 | 18 |
| VADMI-140 | 22 | 16.6 | 18 | G1/4 | G1/8 | 5.2 | M3 | 113.4 | 83.4 | 61.4 | 41.4 | 41.4 | 36 | 17.5 |
| VADMI-200 | 22 | 16.6 | 18 | G3/8 | G1/4 | 5.2 | M3 | 119.4 | 89.4 | 67.7 | 41.4 | 41.4 | 40 | 19 |
| VADMI-300 | 22 | 16.6 | 18 | G3/8 | G1/4 | 5.2 | M3 | 119.4 | 89.4 | 67.7 | 41.4 | 41.4 | 40 | 19 |

| Type | L1 | L2 | L4 | L5 | L6 | L7 | L8 | L9 | L10 | L11 | L12 | L13 | L14 |
|-----------|-------|-------|------|------|------|-----|------|----|-------|------|-----|-------|-----|
| VADMI-45 | 45 | 41 | 33.6 | 25 | 3.6 | 11 | 33 | 55 | 56 | 7.9 | 1.9 | 36.3 | 4 |
| VADMI-70 | 62.3 | 58.3 | 40.4 | 21 | 14.2 | 11 | 45 | 67 | 76.1 | 9.4 | 1.9 | 53.7 | 4.5 |
| VADMI-95 | 65 | 61 | 43.3 | 8.7 | 13.2 | 5.7 | 49.5 | 61 | 78.8 | 9.5 | 2.3 | 55 | 4.5 |
| VADMI-140 | 88 | 84 | 26 | 12.5 | 28.5 | 5.7 | 49.5 | 61 | 96.8 | 13.8 | 2.3 | 79.4 | 5 |
| VADMI-200 | 88 | 84 | 26 | 12.5 | 28.5 | 5.7 | 49.5 | 61 | 101.8 | 12.5 | 2.3 | 79.4 | 5 |
| VADMI-300 | 124.4 | 120.4 | 26 | 12.5 | 28.5 | 5.7 | 49.5 | 61 | 137.4 | 12.5 | 2.3 | 115.8 | 5 |

– Note: This product conforms to ISO 1179-1 and to ISO 228-1

Vacuum generators VADM/VADMI



Technical data

FESTO

Dimensions

VADMI-45/-70-P/-N/-LS-P

VADMI-95/-140/-200/-300-P/-N/-LS-P



- 1 Compressed air port
- 2 Vacuum port
- 3 Manual override facility

- 4 Mounting thread
- 5 Mounting hole
- 7 Suitable socket for:
VADMI-45/-70 and KMYZ-...

VADMI-95/-.../-300
KMEB-... and MSSD-EB
→ Internet: kmeb1
→ Internet: mssd-eb

- 8 Connection for connecting
cable NEBU-M8
→ Internet: nebu-m8

| Type | B1 | B2 | B3 | D1 | D2 | D3 Ø | D4 | H1 | H2 | H3 | H4 | H5 | H6 | H7 |
|----------------|----|------|----|------|------|---------|------|-------|------|------|------|------|------|------|
| VADMI-45-P/-N | 10 | 6.2 | 10 | M5 | M5 | 3.2 | M2 | 78.2 | 58.2 | 40.8 | 23.8 | 23.8 | 43.4 | 18 |
| VADMI-70-P/-N | 15 | 11.2 | 15 | G1/8 | M5 | 3.2 | M2 | 88.9 | 64.4 | 47 | 26.5 | 23.5 | 48.8 | 18 |
| VADMI-95-P/-N | 18 | 13.4 | 18 | G1/8 | G1/8 | 4.2 | M2.5 | 99.4 | 69.4 | 48.9 | 25.5 | 23.3 | 33 | 18 |
| VADMI-140-P/-N | 22 | 16.6 | 18 | G1/4 | G1/8 | 5.2 | M3 | 113.4 | 83.4 | 61.4 | 41.4 | 41.4 | 36 | 17.5 |
| VADMI-200-P/-N | 22 | 16.6 | 18 | G3/8 | G1/4 | 5.2 | M3 | 119.4 | 89.4 | 67.7 | 41.4 | 41.4 | 40 | 19 |
| VADMI-300-P/-N | 22 | 16.6 | 18 | G3/8 | G1/4 | 5.2 | M3 | 119.4 | 89.4 | 67.7 | 41.4 | 41.4 | 40 | 19 |
| VADMI-45-LS-P | 10 | 6.2 | 10 | M5 | M5 | 3.2 | M2 | 78.2 | 58.2 | 40.8 | 23.8 | 23.8 | 43.4 | 18 |
| VADMI-70-LS-P | 15 | 11.2 | 15 | G1/8 | M5 | 3.2 | M2 | 88.9 | 64.4 | 47 | 26.5 | 23.5 | 48.8 | 18 |
| VADMI-95-LS-P | 18 | 13.4 | 18 | G1/8 | G1/8 | 4.2 | M3 | 99.4 | 69.4 | 48.9 | 25.5 | 23.3 | 33 | 18 |
| VADMI-140-LS-P | 22 | 16.6 | 18 | G1/4 | G1/8 | 5.2 | M3 | 113.4 | 83.4 | 61.4 | 41.4 | 41.4 | 36 | 17.5 |
| VADMI-200-LS-P | 22 | 16.6 | 18 | G3/8 | G1/4 | 5.2 | M3 | 119.4 | 89.4 | 67.7 | 41.4 | 41.4 | 40 | 19 |
| VADMI-300-LS-P | 22 | 16.6 | 18 | G3/8 | G1/4 | 5.2 | M3 | 119.4 | 89.4 | 67.7 | 41.4 | 41.4 | 40 | 19 |

| Type | L1 | L2 | L3 | L4 | L5 | L6 | L7 | L8 | L9 | L10 | L11 | L12 | L13 | L14 |
|-----------------------------|-------|-------|------|------|------|------|-----|------|----|-------|------|-----|-------|-----|
| VADMI-45-P/-N | 71.4 | 41 | 28.4 | 33.6 | 25 | 3.6 | 11 | 33 | 55 | 56 | 7.9 | 1.9 | 36.3 | 4 |
| VADMI-70-P/-N | 88.7 | 58.3 | 28.4 | 40.4 | 21 | 14.2 | 11 | 45 | 67 | 76.1 | 9.4 | 1.9 | 53.7 | 4.5 |
| VADMI-95-P/-N | 91.4 | 61 | 28.4 | 43.3 | 8.7 | 13.2 | 5.7 | 49.5 | 61 | 78.8 | 9.5 | 2.3 | 55 | 4.5 |
| VADMI-140-P/-N | 114.4 | 84 | 28.4 | 26 | 12.5 | 28.5 | 5.7 | 49.5 | 61 | 96.8 | 13.8 | 2.3 | 79.4 | 5 |
| VADMI-200-P/-N | 114.4 | 84 | 28.4 | 26 | 12.5 | 28.5 | 5.7 | 49.5 | 61 | 101.8 | 12.5 | 2.3 | 79.4 | 5 |
| VADMI-300-P/-N | 150.8 | 120.4 | 28.4 | 26 | 12.5 | 28.5 | 5.7 | 49.5 | 61 | 137.4 | 12.5 | 2.3 | 115.8 | 5 |
| VADMI-45-LS-P ¹⁾ | 71.4 | 41 | 28.4 | 33.6 | 25 | 3.6 | 11 | 33 | 55 | 56 | 7.9 | 1.9 | 36.3 | 4 |
| VADMI-70-LS-P | 88.7 | 58.3 | 28.4 | 40.4 | 21 | 14.2 | 11 | 45 | 67 | 76.1 | 9.4 | 1.9 | 53.7 | 4.5 |
| VADMI-95-LS-P | 91.4 | 61 | 28.4 | 43.3 | 8.7 | 13.2 | 5.7 | 49.5 | 61 | 78.8 | 9.5 | 2.3 | 55 | 4.5 |
| VADMI-140-LS-P | 114.4 | 84 | 28.4 | 26 | 12.5 | 28.5 | 5.7 | 49.5 | 61 | 96.8 | 13.8 | 2.3 | 79.4 | 5 |
| VADMI-200-LS-P | 114.4 | 84 | 28.4 | 26 | 12.5 | 28.5 | 5.7 | 49.5 | 61 | 101.8 | 12.5 | 2.3 | 79.4 | 5 |
| VADMI-300-LS-P | 150.8 | 120.4 | 28.4 | 26 | 12.5 | 28.5 | 5.7 | 49.5 | 61 | 137.4 | 12.5 | 2.3 | 115.8 | 5 |

¹⁾ Plug sockets are included in the scope of delivery for type ...-LS-....

• Note: This product conforms to ISO 1179-1 and to ISO 228-1


Vacuum generators VADM/VADMI

Technical data

FESTO

| Ordering data | | | | | | | | | |
|-----------------------|----------------|-----------------------|-----------|--------------------|--------|-------------|------------|--------|-------------|
| Size | Solenoid coils | Without vacuum switch | | With vacuum switch | | | | | |
| | | | | PNP output | | | NPN output | | |
| | | Part No. | Type | Part No. | Type | | Part No. | Type | |
| Without ejector pulse | | | | | | | | | |
| 45 | MZB | 162500 | VADM-45 | | 162512 | VADM-45-P | | 162513 | VADM-45-N |
| 70 | MYB | 162501 | VADM-70 | | 162514 | VADM-70-P | | 162515 | VADM-70-N |
| 95 | MEB | 162502 | VADM-95 | | 162516 | VADM-95-P | | 162517 | VADM-95-N |
| 140 | MEB | 162503 | VADM-140 | | 162518 | VADM-140-P | | 162519 | VADM-140-N |
| 200 | MEB | 162504 | VADM-200 | | 162520 | VADM-200-P | | 162521 | VADM-200-N |
| 300 | MEB | 162505 | VADM-300 | | 162522 | VADM-300-P | | 162523 | VADM-300-N |
| | | | | | | | | | |
| With ejector pulse | | | | | | | | | |
| 45 | MZB | 162506 | VADMI-45 | | 162524 | VADMI-45-P | | 162525 | VADMI-45-N |
| 70 | MYB | 162507 | VADMI-70 | | 162526 | VADMI-70-P | | 162527 | VADMI-70-N |
| 95 | MEB | 162508 | VADMI-95 | | 162528 | VADMI-95-P | | 162529 | VADMI-95-N |
| 140 | MEB | 162509 | VADMI-140 | | 162530 | VADMI-140-P | | 162531 | VADMI-140-N |
| 200 | MEB | 162510 | VADMI-200 | | 162532 | VADMI-200-P | | 162533 | VADMI-200-N |
| 300 | MEB | 162511 | VADMI-300 | | 162534 | VADMI-300-P | | 162535 | VADMI-300-N |

| Ordering data | | | | | | | |
|--|----------------|--------------------|----------------|--|--|------------|----------------|
| Size | Solenoid coils | With vacuum switch | | | | | |
| | | PNP output | | | | NPN output | |
| | | Part No. | Type | | | Part No. | Type |
| With ejector pulse and air-saving function | | | | | | | |
| 45 | MZB | 171053 | VADMI-45-LS-P | | | 171054 | VADMI-45-LS-N |
| 70 | MYB | 171055 | VADMI-70-LS-P | | | 171056 | VADMI-70-LS-N |
| 95 | MEB | 171057 | VADMI-95-LS-P | | | 171058 | VADMI-95-LS-N |
| 140 | MEB | 171059 | VADMI-140-LS-P | | | 171060 | VADMI-140-LS-N |
| 200 | MEB | 171061 | VADMI-200-LS-P | | | 171062 | VADMI-200-LS-N |
| 300 | MEB | 171063 | VADMI-300-LS-P | | | 171064 | VADMI-300-LS-N |



Note

With vacuum generators VADMI-...-LS-P/N, the plug sockets with cable for solenoid coils and vacuum switches are included in the scope of supply. These vacuum generators may only be operated with the cable supplied.