

Pneumatic valves VUWG


FESTO



Pneumatic valves VUWG

Key features

FESTO



Innovative

- Various connection sizes (M3, M5, M7, G $\frac{1}{8}$, G $\frac{1}{4}$)
- Max. pressure 10 bar
- 2x3/2-way valve in one valve housing

Versatile

- Wide range of valve functions
- In-line valves can be used as individual valves or manifold valves
- M5/M7 in-line valves can be mixed on one manifold rail
- Identical sub-base valves for M5 or M7 manifold rail
- Manifolds with pressure zones
- Choice of quick push-in connectors

Reliable

- Sturdy and durable metal components
 - Valves
 - Manifold rails
- Reliable servicing thanks to valves that can be replaced quickly and easily

Easy to mount


- Secure mounting on wall or H-rail
- Easy mounting thanks to captive screws and seals

Pneumatic valves VUWG


Key features – Pneumatic components

FESTO


Individual valves and valve manifolds




VUWG-L in-line valve as individual valve




VUWG-S in-line valve for manifold assembly



VUWG-S valve manifold consisting of in-line valves




VUWG-B sub-base valve for manifold assembly



VUWG-B valve manifold consisting of sub-base valves

VUWG basic valves




- Width 10, 14 and 18 mm
- 2x 3/2-way, 5/2-way and 5/3-way valves
- In-line valves
- Sub-base valves

Pneumatic valves VUWG

Key features – Pneumatic components


FESTO

Manifold rail for in-line valves



- For in-line valves M3, M5, M7, G $\frac{1}{8}$ and G $\frac{1}{4}$, width 10/14/18
- For 2x3/2-way, 5/2-way and 5/3-way valves
- 2 to 10 and 12, 14, 16 valve positions

Manifold rail for sub-base valves



- For sub-base valves 10A, 10, 14 and 18, width 10/14/18
- Manifold rail with M3, M5/M7, G $\frac{1}{8}$ and G $\frac{1}{4}$ working ports
- For 2x3/2-way, 5/2-way and 5/3-way valves
- 2 to 10, 12, 14 and 16 valve positions
- The sub-base valves always have external pilot air. The pilot air is set via the manifold rail. A short (for internal pilot air) and long (for external pilot air) blanking plug are included with the manifold rail for this purpose.



Note

Duct 84 must not be sealed by a blanking plug when connecting a sub-base valve.

Blanking plate for vacant position



For covering unused valve positions

Supply plate




For additional air supply and exhaust via a valve position

Separator for pressure zones



For creating multiple pressure zones

Pilot pressure p2 as a function of operating pressure p1



This graph applies to the 2x3/2-way valves and 5/2-way single pilot valves with air spring:

- T32CA, T32UA, T32HA
- M52A, M52R



Note

The compressed air for the air spring is supplied from port 1 (operating pressure). To ensure reliable valve switching, the minimum pressure as per the graph must always be adhered to for the pilot pressure.

Pneumatic valves VUWG

Key features – Pneumatic components

FESTO

Creating pressure zones and separating exhaust air

Compressed air is supplied and exhausted via the manifold rail and supply plates.

The position of the supply plates and duct separations can be freely selected with the VUWG.

Pressure zones are created by isolating the internal supply ducts between the manifold sub-bases by means of appropriate duct separation.

Pressure zone separation can be used for the following ducts:

- Duct 1
- Duct 3
- Duct 5




Note

- Use separators if the exhaust air pressures are high
- Use at least one supply plate/supply for each pressure zone

Duct separation

	Description	Symbol
	The pressure zones can be freely configured with the VUWG. The following duct separations are possible:	
	• Duct 1 closed	
	• Duct 1/3/5 closed	
	• Duct 3/5 closed	
	The number of pressure zones with the VUWG is only limited by the number of valve positions on the manifold rail. Note that each supply plate occupies one valve position.	

Separator VABD



Note


As the separators are mounted from only one side using a slotted screwdriver, several pressure zones can be created in one profile.

Pneumatic valves VUWG

Key features – Pneumatic components

FESTO

Flow control valve



- 1 Valve
- 2 Flow control valve
- 3 Fitting

Flow control mountable on port 1, 3/5 and/or on port 2/4.

Operation with different pressures

Vacuum operation

Note the following with vacuum operation:


- M52 in-line valves with pneumatic spring and pneumatic/mechanical spring reset (vacuum only at 3/5)
- T32 valves with pneumatic spring reset (vacuum only at 3/5)

If external pilot air via duct 14 is used, M52 sub-base valves (B) can be used without restriction.

The remaining valve types can be used without restriction for vacuum.

Reverse operation


The valves with pneumatic spring are not suitable for reverse operation, since at least the minimum pilot pressure must be present in duct 1.



Note

Pressure must be present at port 1.

Pressure deflector (internal pilot air)



- If two different pressures are required.

- Different pressures can be supplied at duct 1, 3 and 5.



Note

- With internal pilot air, the minimum pilot pressure must be adhered to in duct 1


- With 2x3/2-way valves without spring return, the minimum pilot pressure must always be adhered to in duct 1

Advantages

Any pressure or vacuum can be connected at ducts 3 and 5 both with

external and internal pilot air.

Vacuum, ejector pulse and normal position





Vacuum, ejector pulse and normal position with internal pilot air can be achieved by connecting vacuum


at duct 3 and pressure for the ejector pulse at duct 1.



Pneumatic valves VUWG

Product range overview

FESTO

Design	Working port	Valve code	Functions and flow rate [l/min]												→ Page/ Internet
			T32C	T32U	T32H	T32C/M	T32U/M	T32H/M	M52	M52/M	B52	P53C	P53U	P53E	
In-line valve as individual valve, VUWG-L															
	M3	10A	–	–	–	–	–	–	■	■	■	■	■	■	12
	M5	10	■	■	■	■	■	■	■	■	■	■	■	■	18
	M7	10	■	■	■	■	■	■	■	■	■	■	■	■	18
	G1/8	14	■	■	■	■	■	■	■	■	■	■	■	■	28
	G1/4	18	■	■	■	■	■	■	■	■	■	■	■	■	35
In-line valve for manifold assembly, VUWG-S															
	M3	10A	–	–	–	–	–	–	■	■	■	■	■	■	15
	M5	10	■	■	■	■	■	■	■	■	■	■	■	■	25
	M7	10	■	■	■	■	■	■	■	■	■	■	■	■	25
	G1/8	14	■	■	■	■	■	■	■	■	■	■	■	■	32
	G1/4	18	■	■	■	■	■	■	■	■	■	■	■	■	39

Design	Working port	Type code	Functions and flow rate [l/min]												→ Page/ Internet
			T32C	T32U	T32H	T32C/M	T32U/M	T32H/M	M52	M52/M	B52	P53C	P53U	P53E	
Sub-base valve, VUWG-B															
	–	10 A	–	–	–	–	–	–	■	■	■	■	■	■	42
	–	10	■	■	■	■	■	■	■	■	■	■	■	■	47
	–	10	■	■	■	■	■	■	■	■	■	■	■	■	47
	–	14	■	■	■	■	■	■	■	■	■	■	■	■	52
	–	18	■	■	■	■	■	■	■	■	■	■	■	■	57

Design	Working port	Type code	Description	→ Page/ Internet
Manifold rail VABM- ... -S- ... , for in-line valves (manifold assembly)				
	–	–	Valve size M3, M5, M7, G1/8, G1/4	vabm
Manifold rail VABM, for sub-base valves				
	–	10AW	Connection size M3	vabm
	–	10W	Connection size M5	
	–	10HW	Connection size M7	
	–	14W	Connection size G1/8	
	–	18W	Connection size G1/4	

Pneumatic valves VUWG

Overview of valve functions




FESTO

Valve	Valve code	Description	Valve terminal/ position function order code	Size			
				M3	M5/M7	G1/8	G1/4
2x 3/2-way valve, normally closed, pneumatic spring							
	T32C-A	External pilot air supply	K	-	■	■	■
2x 3/2-way valve, normally open, pneumatic spring							
	T32U-A	External pilot air supply	N	-	■	■	■
2x 3/2-way valve, 1x normally open, 1x normally closed, pneumatic spring							
	T32H-A	External pilot air supply	H	-	■	■	■
2x 3/2-way valve, normally closed, mechanical spring							
	T32C-M	External pilot air supply	VK	-	■	■	■
2x 3/2-way valve, normally open, mechanical spring							
	T32U-M	External pilot air supply	VN	-	■	■	■
2x 3/2-way valve, 1x normally open, 1x normally closed, mechanical spring							
	T32H-M	External pilot air supply	VH	-	■	■	■
5/2-way valve, double pilot							
	B52	External pilot air supply	J	■	■	■	■
5/2-way valve, single pilot, mechanical spring							
	M52-M	External pilot air supply	A	■	■	■	■
5/2-way valve, single pilot, pneumatic spring							
	M52-A	In-line valve, external pilot air supply	M	-	-	■	-
5/2-way valve, single pilot, pneumatic/mechanical spring							
	M52-R	In-line valve, external pilot air supply	P	■	■	-	■
5/2-way valve, single pilot, pneumatic spring							
	M52-A	Sub-base valve, external pilot air supply	M	-	-	■	-
5/2-way valve, single pilot, pneumatic/mechanical spring							
	M52-R	Sub-base valve, external pilot air supply	P	■	■	-	■

Pneumatic valves VUWG

Overview of valve functions




Valve	Valve code	Description	Valve terminal/ position function order code	Size			
				M3	M5/M7	G1/8	G1/4
5/3-way valve, mid-position closed							
	P53C	External pilot air supply	G	☐	☐	☐	☐
5/3-way valve, mid-position pressurised							
	P53U	External pilot air supply	B	☐	☐	☐	☐
5/3-way valve, mid-position exhausted							
	P53E	External pilot air supply	E	☐	☐	☐	☐

Pneumatic valves VUWG

Sample system overview – VUWG-L10 and VUWG-S10, in-line valves M5/M7

FESTO

Manifold assembly




Manifold assembly and accessories			
	Type	Brief description	→ Page/Internet
1	Manifold rail	VABM-L1-10S-G18	For 2 to 10, 12, 14 and 16 valve positions
2	Blanking plate	VABB-L1-10-S	For covering an unused valve position
3	Supply plate	VABF-L1-10-P3A4	For air supply port 1 and ports 3 and 5
4	Pneumatic valve	VUWG	Single pilot pneumatic valve
5	Pneumatic valve	VUWG	Double pilot pneumatic valve
6	Push-in fitting	QS	For adapter plate for port 12 or 14
7	H-rail	NRH-35-2000	For mounting the valve manifold
8	H-rail mounting	VAME-T-M4	2 pieces for fitting the valve manifold on an H-rail
9	Separator	VABD-8-B	For creating pressure zones
10	Silencer	U	For port 3
11	Push-in fitting	QS	For port 1
12	Silencer	U	For port 5
13	Push-in fitting	QS	For ports 2 and 4

Pneumatic valves VUWG

Sample system overview – VUWG-B10, sub-base valves

FESTO

Manifold assembly



Manifold assembly and accessories			
	Type	Brief description	→ Page/Internet
1	Manifold rail	VABM-L1-10W-G18	For 2 to 10, 12, 14 and 16 valve positions
2	Blanking plate	VABB-L1-10-W	For covering an unused valve position
3	Supply plate	VABF-L1-10-P3A4-M5	For air supply port 1 and ports 3 and 5
4	Pneumatic valve	VUWG	Single pilot pneumatic valve
5	Pneumatic valve	VUWG	Double pilot pneumatic valve
6	Push-in fitting	QS	For adapter plate for port 12 or 14
7	H-rail	NRH-35-2000	For mounting the valve manifold
8	H-rail mounting	VAME-T-M4	2 pieces for fitting the valve manifold on an H-rail
9	Separator	VABD-6-B	For creating pressure zones
10	Silencer	U	For port 84
11	Push-in fitting	QS	For port 14
12	Silencer	U	For port 5
13	Push-in fitting	QS	For port 1
14	Silencer	U	For port 3
15	Push-in fitting	QS	For ports 2 and 4

Pneumatic valves VUWG-L10A, in-line valves M3

FESTO

Technical data

Function

5/2-way, single pilot
5/2-way, double pilot
5/3C, 5/3U, 5/3E

-  - Width 10 mm

-  - Flow rate
80 ... 100 l/min



General technical data						
Valve function	M52-R	B52	M52-M	P53		
Normal position	–	–	–	C ¹⁾	U ²⁾	E ³⁾
Pneumatic spring reset method	Yes ⁴⁾	–	No	No		
Mechanical spring reset method	Yes ⁴⁾	–	Yes	Yes		
Vacuum operation at port 1	No	Yes	Yes	Yes		
Vacuum operation at port 3/5	Yes					
Design	Piston spool valve					
Sealing principle	Soft					
Actuation type	Pneumatic					
Type of control	Direct					
Pilot air supply	External					
Exhaust function	With flow control					
Type of mounting	Optionally via through-holes ⁶⁾ or on manifold rail					
Mounting position	Any					
Standard nominal flow rate	[l/min]	100		80	90	
Switching time on/off	[ms]	5/11	–	5/16	7/19	
Changeover time	[ms]	–	5	–	9	
Width	[mm]	10				
Port	1, 2, 3, 4, 5	M3				
	12, 14	M5				
Product weight	[g]	37	40	34	40	
Corrosion resistance class CRC ⁵⁾	2					

1) C = Normally closed

2) U = Normally open/mid-position pressurised

3) E = Normally exhausted

4) Combined reset method

5) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

6) If several valves are to be screwed together via the through-holes to form a block, a minimum gap of 0.3 mm must be ensured by placing spacer discs between them.

Operating and environmental conditions				
Valve function	M52-R ³⁾	B52	M52-M ²⁾	P53
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]			
Note on operating/pilot medium	Lubricated operation possible (required during subsequent operation)			
Operating pressure	[bar]	2.5 ... 10	–0.9 ... 10	–0.9 ... 8
Pilot pressure ¹⁾	[bar]	2.5 ... 10	1.5 ... 10	3 ... 10
Ambient temperature	[°C]	–5 ... +60		
Temperature of medium	[°C]	–5 ... +50		

1) Note operating pressure/pilot pressure graph → page 4

2) Mechanical spring

3) Mixed, pneumatic/mechanical spring

Pneumatic valves VUWG-L10A, in-line valves M3


FESTO

Technical data

Information on materials	
Housing	Anodised aluminium
Seals	HNBR, NBR
Note on materials	RoHS-compliant

Dimensions Download CAD data → www.festo.com


5/2-way and 5/3-way valve



Type	B1	B2	D1	D2	H1	H2	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10
VUWG-L10A-...	10.3	3.6	M3	3.2	32.5	9.1	59.9	50.7	34.9	18.5	20.7	7	9	7.9	7.3	12.4
VUWG-L10A-M52-...							49.9									

Ordering data			
	Description	Part No.	Type
In-line valve M3			
	5/2-way valve, monostable		
	External pilot air supply, reset method: mechanical/pneumatic spring	573795	VUWG-L10A-M52-R-M3
	External pilot air supply, reset method: mechanical spring	574250	VUWG-L10A-M52-M-M3
	5/2-way valve, bistable		
	External pilot air supply	573796	VUWG-L10A-B52-M3
	5/3-way valve		
	Mid-position closed, external pilot air supply	573797	VUWG-L10A-P53C-M3
	Mid-position exhausted, external pilot air supply	573798	VUWG-L10A-P53E-M3
	Mid-position pressurised, external pilot air supply	573799	VUWG-L10A-P53U-M3

FESTO

[illegible]

- Subject to change – 2016/03

Pneumatic valves VUWG-S10A, in-line valves M3

FESTO


Manifold assembly

In-line valves for
manifold assembly



Dimensions

Download CAD data → www.festo.com



- 1 Blanking plate
VABB-L1-10A-S
- 2 Supply plate
VABF-L1-10A-P3A4-M5

- 3 Single pilot pneumatic valve
- 4 Double pilot pneumatic valve

- 5 H-rail mounting (two M4x15
screws to DIN 912 are required
for mounting)

Type	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	D1
VABM-L1-10AS-M5	59.9	49.9	29.7	18.7	7.7	2.95	40.3	6.75	24.2	34	25.9	M5


Type	D2	H1	H2	H3	H4	H5	H6	L3	L5	L6	L7	L8	L9
VABM-L1-10AS-M5	Ø 4.5	42.5	10	5.5	16.2	6.8	20.3	7	12.5	10.3	10.5	3.5	14

Valve positions	2	3	4	5	6	7	8	9	10	12	14	16
L1 [mm]	42.5	53	63.5	74	84.5	95	105.5	116	126.5	147.5	168.5	189.5
L2 [mm]	28.5	39	49.5	60	70.5	81	91.5	102	112.5	133.5	154.5	175.5
L4 [mm]	35.5	46	56.5	67	77.5	88	98.5	109	119.5	140.5	161.5	182.5

Pneumatic valves VUWG-S10A, in-line valves M3

FESTO

Ordering data

Technical data – Manifold rails							
	Port	CRC	Material ²⁾	Operating pressure [bar]	Max. tightening torque for assembly [Nm]		
	1, 3, 5				Valve	H-rail	Wall
	M5	2 ¹⁾	Wrought aluminium alloy	-0.9 ... 10	0.45	1.5	3




- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 2) Note on materials: RoHS-compliant.

Order code – Manifold rails							
VABM	-	L1	-	10A	S	-	M5
Manifold assembly parts							
Manifold rail	VABM						
Valve series							
VUWG	L1						
Valve width							
10 mm				10A			
Manifold rail with ports 1, 3, 5							
For M3 in-line valves					S		

Pneumatic valves VUWG-S10A, in-line valves M3

FESTO

Ordering data

Ordering data – Accessories				
	Description		Part No.	Type
Manifold rail for in-line valves (manifold assembly)				
	For valve size M3	2 valve positions	566522	VABM-L1-10AS-M5-2
		3 valve positions	566523	VABM-L1-10AS-M5-3
		4 valve positions	566524	VABM-L1-10AS-M5-4
		5 valve positions	566525	VABM-L1-10AS-M5-5
		6 valve positions	566526	VABM-L1-10AS-M5-6
		7 valve positions	566527	VABM-L1-10AS-M5-7
		8 valve positions	566528	VABM-L1-10AS-M5-8
		9 valve positions	566529	VABM-L1-10AS-M5-9
		10 valve positions	566530	VABM-L1-10AS-M5-10
		12 valve positions	566531	VABM-L1-10AS-M5-12
		14 valve positions	566532	VABM-L1-10AS-M5-14
		16 valve positions	566533	VABM-L1-10AS-M5-16
Blanking plate				
	For manifold rail for M3 in-line valves	Incl. screws and seal	569986	VABB-L1-10A
Separator				
	For manifold rail for M3 in-line valves	Separator for pressure zones	570872	VABD-4.2-B
Supply plate				
	For manifold rail for M3 in-line valves	Incl. screws and seal	569990	VABF-L1-10A-P3A4-M5
Seals for in-line valves				
	M3	Delivery unit: 10 sets (each with 2 screws and 1 seal)	566670	VABD-L1-10AX-S-M3

Pneumatic valves VUWG-L10 and VUWG-S10, in-line valves M5

FESTO

Technical data

Function

2x3/2C, 2x3/2U, 2x3/2H

5/2-way, single pilot

5/2-way, double pilot

5/3C, 5/3U, 5/3E

-  - Width 10 mm

-  - Flow rate
125 ... 220 l/min



General technical data														
Valve function			T32-A			T32-M			M52-R	B52	M52-M	P53		
Normal position			C ¹⁾	U ²⁾	H ⁴⁾	C ¹⁾	U ²⁾	H ⁴⁾	–	–	–	C ¹⁾	U ²⁾	E ³⁾
Pneumatic spring reset method			Yes			No			Yes ⁵⁾	–	No	No		
Mechanical spring reset method			No			Yes			Yes ⁵⁾	–	Yes	Yes		
Vacuum operation at port 1			No			Yes			No	Yes				
Vacuum operation at port 3/5			Yes											
Design			Piston spool valve											
Sealing principle			Soft											
Actuation type			Pneumatic											
Type of control			Direct											
Pilot air supply			External											
Exhaust function			With flow control											
Type of mounting			Optionally via through-holes ⁷⁾ or on manifold rail											
Mounting position			Any											
Standard nominal flow rate		[l/min]	150		135	125		220		190	210			
Switching time on/off		[ms]	4/9		6/7		6/12		–	7/16	8/25			
Changeover time		[ms]	–							5	–	11		
Width		[mm]	10											
Port		1, 2, 3, 4, 5	M5											
		12, 14	M5											
Product weight		[g]	48		51			45	48	41	48			
Corrosion resistance class CRC ⁶⁾			2											

1) C = Normally closed

2) U = Normally open/mid-position pressurised

3) E = Normally exhausted

4) H = 2x 3/2-way valve in one housing with 1x normally closed and 1x normally open

5) Combined reset method

6) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

7) If several valves are to be screwed together via the through-holes to form a block, a minimum gap of 0.3 mm must be ensured by placing spacer discs between them.

Pneumatic valves VUWG-L10 and VUWG-S10, in-line valves M5

FESTO

Technical data

Operating and environmental conditions						
Valve function	T32-A ²⁾	T32-M ³⁾	M52-R ⁴⁾	B52	M52-M ³⁾	P53
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]					
Note on operating/pilot medium	Lubricated operation possible (required during subsequent operation)					
Operating pressure [bar]	1.5 ... 10	-0.9 ... 10	2.5 ... 10	-0.9 ... 10	-0.9 ... 8	-0.9 ... 10
Pilot pressure ¹⁾ [bar]	1.5 ... 10	3 ... 10	2.5 ... 10	1.5 ... 10	3 ... 10	
Ambient temperature [°C]	-5 ... +60					
Temperature of medium [°C]	-5 ... +50					

1) Note operating pressure/pilot pressure graph → page 4

2) Pneumatic spring


3) Mechanical spring

4) Mixed, pneumatic/mechanical spring

Information on materials	
Housing	Wrought aluminium alloy
Seals	HNBR, NBR
Note on materials	RoHS-compliant

Dimensions Download CAD data → www.festo.com

2x3/2-way, 5/2-way and 5/3-way valve




Type	B1	D1	H1	H2	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10
VUWG-L10-...	10.2	3.2	32.5	9.1	72	62.8	47	27	22.5	11	11	7.9	12	16
VUWG-L10-M52-...					62									

Pneumatic valves VUWG-L10 and VUWG-S10, in-line valves M5

FESTO

Technical data

Ordering data		Part No.	Type
Description			
In-line valve M5			
	2x3/2-way valve		
	Normally closed, external pilot air supply, reset method: pneumatic spring	573805	VUWG-L10-T32C-A-M5
	Normally open, external pilot air supply, reset method: pneumatic spring	573806	VUWG-L10-T32U-A-M5
	1x normally open, 1x normally closed, external pilot air supply, reset method: pneumatic spring	573807	VUWG-L10-T32H-A-M5
	Normally closed, external pilot air supply, reset method: mechanical spring	574251	VUWG-L10-T32C-M-M5
	Normally open, external pilot air supply, reset method: mechanical spring	574252	VUWG-L10-T32U-M-M5
	1x normally open, 1x normally closed, external pilot air supply, reset method: mechanical spring	574253	VUWG-L10-T32H-M-M5
	5/2-way valve, monostable		
	External pilot air supply, reset method: pneumatic/mechanical spring	573808	VUWG-L10-M52-R-M5
	External pilot air supply, reset method: mechanical spring	574254	VUWG-L10-M52-M-M5
	5/2-way valve, bistable		
	External pilot air supply	573809	VUWG-L10-B52-M5
	5/3-way valve		
	Mid-position closed, external pilot air supply	573810	VUWG-L10-P53C-M5
	Mid-position exhausted, external pilot air supply	573811	VUWG-L10-P53E-M5
	Mid-position pressurised, external pilot air supply	573812	VUWG-L10-P53U-M5

Pneumatic valves VUWG-L10 and VUWG-S10, in-line valves M7

FESTO

Technical data

Function

2x3/2C, 2x3/2U, 2x3/2H

5/2-way, single pilot

5/2-way, double pilot

5/3C, 5/3U, 5/3E

-  - Width 10 mm

-  - Flow rate
140 ... 380 l/min



General technical data														
Valve function			T32-A			T32-M			M52-R	B52	M52-M	P53		
Normal position			C ¹⁾	U ²⁾	H ⁴⁾	C ¹⁾	U ²⁾	H ⁴⁾	–	–	–	C ¹⁾	U ²⁾	E ³⁾
Pneumatic spring reset method			Yes			No			Yes ⁵⁾	–	No	No		
Mechanical spring reset method			No			Yes			Yes ⁵⁾	–	Yes	Yes		
Vacuum operation at port 1			No			Yes			No	Yes				
Vacuum operation at port 3/5			Yes											
Design			Piston spool valve											
Sealing principle			Soft											
Actuation type			Pneumatic											
Type of control			Direct											
Pilot air supply			External											
Exhaust function			With flow control											
Type of mounting			Optionally via through-holes ⁷⁾ or on manifold rail											
Mounting position			Any											
Standard nominal flow rate		[l/min]	190			150	140		380		320			
Switching time on/off		[ms]	4/9			6/7		6/12		–	7/16	8/25		
Changeover time		[ms]	–			–					5	–	11	
Width		[mm]	10											
Port		1, 2, 3, 4, 5	M7											
		12, 14	M5											
Product weight		[g]	48			51		45		48	41	48		
Corrosion resistance class CRC ⁶⁾			2											

1) C = Normally closed

2) U=Normally open/mid-position pressurised

3) E = Normally exhausted

4) H=2x 3/2-way valve in one housing with 1x normally closed and 1x normally open

5) Combined reset method

6) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

7) If several valves are to be screwed together via the through-holes to form a block, a minimum gap of 0.3 mm must be ensured by placing spacer discs between them.

Pneumatic valves VUWG-L10 and VUWG-S10, in-line valves M7

FESTO

Technical data

Operating and environmental conditions						
Valve function	T32-A ²⁾	T32-M ³⁾	M52-R ⁴⁾	B52	M52-M ³⁾	P53
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]					
Note on operating/pilot medium	Lubricated operation possible (required during subsequent operation)					
Operating pressure [bar]	1.5 ... 10	-0.9 ... 10	2.5 ... 10	-0.9 ... 10	-0.9 ... 8	-0.9 ... 10
Pilot pressure ¹⁾ [bar]	1.5 ... 10	3 ... 10	2.5 ... 10	1.5 ... 10	3 ... 10	
Ambient temperature [°C]	-5 ... +60					
Temperature of medium [°C]	-5 ... +50					

1) Note operating pressure/pilot pressure graph → page 4

2) Pneumatic spring

3) Mechanical spring


4) Mixed, pneumatic/mechanical spring

Information on materials	
Housing	Wrought aluminium alloy
Seals	HNBR, NBR
Note on materials	RoHS-compliant

Dimensions

Download CAD data → www.festo.com

2x3/2-way, 5/2-way and 5/3-way valve




Type	B1	D1	H1	H2	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10
VUWG-L10-...	10.2	3.2	32.5	9.1	72	62.8	47	27	22.5	11	11	7.9	12	16
VUWG-L10-M52-...					62									

Pneumatic valves VUWG-L10 and VUWG-S10, in-line valves M7

FESTO


Technical data









Ordering data			
	Description	Part No.	Type
In-line valve M7			
	2x3/2-way valve		
	Normally closed, external pilot air supply, reset method: pneumatic spring	573821	VUWG-L10-T32C-A-M7
	Normally open, external pilot air supply, reset method: pneumatic spring	573822	VUWG-L10-T32U-A-M7
	1x normally open, 1x normally closed, external pilot air supply, reset method: pneumatic spring	573823	VUWG-L10-T32H-A-M7
	Normally closed, external pilot air supply, reset method: mechanical spring	574255	VUWG-L10-T32C-M-M7
	Normally open, external pilot air supply, reset method: mechanical spring	574256	VUWG-L10-T32U-M-M7
	1x normally open, 1x normally closed, external pilot air supply, reset method: mechanical spring	574257	VUWG-L10-T32H-M-M7
	5/2-way valve, monostable		
	External pilot air supply, reset method: pneumatic/mechanical spring	573824	VUWG-L10-M52-R-M7
	External pilot air supply, reset method: mechanical spring	574258	VUWG-L10-M52-M-M7
	5/2-way valve, bistable		
	External pilot air supply	573825	VUWG-L10-B52-M7
	5/3-way valve		
	Mid-position closed, external pilot air supply	573826	VUWG-L10-P53C-M7
	Mid-position exhausted, external pilot air supply	573827	VUWG-L10-P53E-M7
	Mid-position pressurised, external pilot air supply	573828	VUWG-L10-P53U-M7

Pneumatic valves VUWG-L10 and VUWG-S10, in-line valves M5/M7

FESTO

Order code

VUWG	-	10	-
Valve design			
In-line, individual valve		L	
			
In-line valve, manifold valve incl. seal and screws		S	
			
Width			
10 mm		10	

Valve functions	
	T32C
	T32U
	T32H
	M52
	B52
	P53C
	P53U
	P53E

- 1) If Q... is chosen for the pneumatic connection, this also applies to the exhaust ports 3 and 5
- 2) Flow rate applies to 5/2-way individual valve

Exhausting with VUWG-L	
QN	QS if QS ¹⁾
U	Silencer
-	M5 and M7
Pneumatic connection	
M5	Thread M5
Q3	Push-in connector 3 mm/M5
Q4	Push-in connector 4 mm/M5
Q6	Push-in connector 6 mm/M5
T14	Push-in connector 1/4"
T18	Push-in connector 1/8"
T316	Push-in connector 3/16"
T532	Push-in connector 5/32"
M7	Thread M7
Q4H	Push-in connector 4 mm/M7
Q6H	Push-in connector 6 mm/M7
T14H	Push-in connector 1/4", M7
T316H	Push-in connector 3/16", M7
Flow rate [l/min] ²⁾	
	220
	100
	200
	220
	100
	200
	200
	380
	220
	330
	330
	200
Reset method	
A	Pneumatic spring for T32 and M52
M	Mechanical spring for T32 and M52
R	Pneu./mech. spring for M52
-	With B52 and P53

Pneumatic valves VUWG-S10, in-line valves M5/M7

FESTO


Manifold assembly

In-line valves for
manifold assembly



Dimensions

Download CAD data → www.festo.com



- 1 Pneumatic valve
 2 Supply plate M5 or M7 for 1, 3, 5
 3 Blanking plate VABB-L1-10-S
 4 H-rail mounting (two M4x20 screws to DIN 912 are required)

Type	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11
VABM-L1-10S-G18	72	62	41	24.5	8	52	16.5	16	26.5	29.5	14.45


Type	D1	D2	H1	H2	H3	H4	H4	L3	L4	L5	L6	L7
VABM-L1-10S-G18	G $\frac{1}{8}$	4.5	49.3	16.8	7	16.2	16.2	9	19	10.5	10.3	2

Valve positions	2	3	4	5	6	7	8	9	10	12	14	16	22
L1 [mm]	48.5	59	69.5	80	90.5	101	111.5	122	132.5	153.5	174.5	195.5	258.5
L2 [mm]	30.5	41	51.5	62	72.5	83	93.5	104	114.5	135.5	156.5	177.5	240.5

Pneumatic valves VUWG-S10, in-line valves M5/M7


FESTO

Ordering data

Technical data – Manifold rails							
	Port	CRC	Material ²⁾	Operating pressure [bar]	Max. tightening torque for assembly [Nm]		
	1, 3, 5				Valve	H-rail	Wall
	G1/8	2 ¹⁾	Wrought aluminium alloy	-0.9 ... 10	0.45	1.5	3

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 2) Note on materials: RoHS-compliant.

Order code – Manifold rails							
VABM	-	L1	-	10	S	-	G18
Manifold assembly parts							Number of valve positions
Manifold rail	VABM						2 to 10, 12, 14 and 16
Valve series							Ports 1, 3, 5
VUWG	L1						G18 G1/8
Valve width							
10 mm				10			
Manifold rail with ports 1, 3, 5							
For M5 and M7 in-line valves					S		

Ordering data – Manifold rail			
	Description	Part No.	Type
Manifold rail for in-line valve (manifold assembly)			
	For valve size M5/M7	2 valve positions	566558 VABM-L1-10S-G18-2
		3 valve positions	566559 VABM-L1-10S-G18-3
		4 valve positions	566560 VABM-L1-10S-G18-4
		5 valve positions	566561 VABM-L1-10S-G18-5
		6 valve positions	566562 VABM-L1-10S-G18-6
		7 valve positions	566563 VABM-L1-10S-G18-7
		8 valve positions	566564 VABM-L1-10S-G18-8
		9 valve positions	566565 VABM-L1-10S-G18-9
		10 valve positions	566566 VABM-L1-10S-G18-10
		12 valve positions	566567 VABM-L1-10S-G18-12
		14 valve positions	566568 VABM-L1-10S-G18-14
		16 valve positions	566569 VABM-L1-10S-G18-16

Pneumatic valves VUWG-S10, in-line valves M5/M7

FESTO

Ordering data

Ordering data – Accessories				
	Description		Part No.	Type
Blanking plate			Technical data ➔ Internet: vabb	
	For manifold rail for M5/M7 in-line valves	Incl. screws and seal	566462	VABB-L1-10-S
Separator			Technical data ➔ Internet: vabd	
	For manifold rail for M5/M7 in-line valves	Separator for pressure zones	569995	VABD-8-B
Supply plate			Technical data ➔ Internet: vabf	
	For manifold rail for M5 in-line valves	Incl. screws and seal	569991	VABF-L1-10-P3A4-M5
	For manifold rail for M7 in-line valves		569992	VABF-L1-10-P3A4-M7
Seals for in-line valves			Technical data ➔ Internet: vabd	
	M5	Delivery unit: 10 sets (each with 2 screws and 1 seal)	566672	VABD-L1-10X-S-M5
	M7		566673	VABD-L1-10X-S-M7

Pneumatic valves VUWG-L14 and VUWG-S14, in-line valves G1/8

FESTO

Technical data

Function

2x3/2C, 2x3/2U, 2x3/2H

5/2-way, single pilot

5/2-way, double pilot

5/3C, 5/3U, 5/3E

-  - Width 14 mm

-  - Flow rate
500 ... 780 l/min



General technical data													
Valve function	T32-A			T32-M			M52-A	B52	M52-M	P53			
Normal position	C ¹⁾	U ²⁾	H ⁴⁾	C ¹⁾	U ²⁾	H ⁴⁾	–	–	–	C ¹⁾	U ²⁾	E ³⁾	
Pneumatic spring reset method	Yes			No			Yes	–	No	No			
Mechanical spring reset method	No			Yes			No	–	Yes	Yes			
Vacuum operation at port 1	No			Yes			No	Yes					
Vacuum operation at port 3/5	Yes												
Design	Piston spool valve												
Sealing principle	Soft												
Actuation type	Pneumatic												
Type of control	Direct												
Pilot air supply	External												
Exhaust function	With flow control												
Type of mounting	Optionally via through-holes ⁶⁾ or on manifold rail												
Mounting position	Any												
Standard nominal flow rate	[l/min]	650	600	650	550	500	780			650	600		
Switching time on/off	[ms]	6/19			9/13		12/22	–	12/32	8/30			
Changeover time	[ms]	–						6		–	16		
Width	[mm]	14											
Port	1, 2, 3, 4, 5	G1/8											
	12, 14	M5											
Product weight	[g]	81			77		75	81	67	81			
Corrosion resistance class CRC ⁵⁾	2												

1) C = Normally closed

2) U = Normally open/mid-position pressurised

3) E = Normally exhausted

4) H = 2x3/2-way valve in one housing with 1x normally closed and 1x normally open

5) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

6) If several valves are to be screwed together via the through-holes to form a block, a minimum gap of 0.3 mm must be ensured by placing spacer discs between them.

Pneumatic valves VUWG-L14 and VUWG-S14, in-line valves G1/8

FESTO

Technical data

Operating and environmental conditions						
Valve function	T32-A ²⁾	T32-M ³⁾	M52-A ²⁾	B52	M52-M ³⁾	P53
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]					
Note on operating/pilot medium	Lubricated operation possible (required during subsequent operation)					
Operating pressure [bar]	1.5 ... 10	-0.9 ... 10	2.5 ... 10	-0.9 ... 10	-0.9 ... 8	-0.9 ... 10
Pilot pressure ¹⁾ [bar]	1.5 ... 10	3 ... 10	2.5 ... 10	1.5 ... 10	3 ... 10	
Ambient temperature [°C]	-5 ... +60					
Temperature of medium [°C]	-5 ... +50					


1) Note operating pressure/pilot pressure graph → page 4

2) Pneumatic spring

3) Mechanical spring

Information on materials	
Housing	Wrought aluminium alloy
Seals	HNBR, NBR
Note on materials	RoHS-compliant

Dimensions	Download CAD data → www.festo.com
2x3/2-way, 5/2-way and 5/3-way valve	




Type	B1	D1	H1	H2	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10
VUWG-L14-...	14.4	3.2	34.8	10.8	92.6	83.4	66.5	37	28.8	14.9	18.35	8.45	18	24.25
VUWG-L14-M52-...					82.25									

Pneumatic valves VUWG-L14 and VUWG-S14, in-line valves G1/8

FESTO

Technical data

Ordering data		Part No.	Type
Description			
In-line valve G1/8			
	2x3/2-way valve		
	Normally closed, external pilot air supply, reset method: pneumatic spring	573829	VUWG-L14-T32C-A-G18
	Normally open, external pilot air supply, reset method: pneumatic spring	573830	VUWG-L14-T32U-A-G18
	1x normally open, 1x normally closed, external pilot air supply, reset method: pneumatic spring	573831	VUWG-L14-T32H-A-G18
	Normally closed, external pilot air supply, reset method: mechanical spring	574259	VUWG-L14-T32C-M-G18
	Normally open, external pilot air supply, reset method: mechanical spring	574260	VUWG-L14-T32U-M-G18
	1x normally open, 1x normally closed, external pilot air supply, reset method: mechanical spring	574261	VUWG-L14-T32H-M-G18
	5/2-way valve, monostable		
	External pilot air supply, reset method: pneumatic/mechanical spring	573832	VUWG-L14-M52-A-G18
	External pilot air supply, reset method: mechanical spring	574262	VUWG-L14-M52-M-G18
	5/2-way valve, bistable		
	External pilot air supply	573833	VUWG-L14-B52-G18
	5/3-way valve		
	Mid-position closed, external pilot air supply	573834	VUWG-L14-P53C-G18
	Mid-position exhausted, external pilot air supply	573835	VUWG-L14-P53E-G18
	Mid-position pressurised, external pilot air supply	573836	VUWG-L14-P53U-G18

FESTO

VUWG	-	14
Valve design		
In-line, individual valve	L	
In-line valve, manifold valve incl. seal and screws	S	
Width		
14 mm		14
Valve functions		
		T32C
		T32U
		T32H
		M52
		B52
		P53C
		P53U
		P53E

2) Flow rate applies to 5/2-way individual valve

Pneumatic valves VUWG-S14, in-line valves G1/8

Manifold assembly


FESTO

In-line valves for
manifold assembly



Dimensions

Download CAD data → www.festo.com



- | | | |
|--|---------------------------------------|--|
| 1 Blanking plate
VABB-L1-14 | 3 Double pilot pneumatic valve | 5 H-rail mounting
(two M4x25 screws to DIN 912
are required for mounting) |
| 2 Supply plate
VABF-L1-14-P3A4-G18 | 4 Single pilot pneumatic valve | |

Type	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	D1
VABM-L1-14S-G14	92.6	82.3	56.6	36.5	16.4	4.5	72.9	26.45	20	36.3	36.3	G1/4


Type	D2	H1	H2	H3	H4	H5	L3	L5	L6	L7
VABM-L1-14S-G14	Ø 4.5	54.8	20	10.6	15.4	26.4	7	2	16	17

Valve positions	2	3	4	5	6	7	8	9	10	12	14	16
L1 [mm]	54	70	86	98	118	134	150	166	182	214	246	278
L2 [mm]	40	56	72	88	104	120	136	152	168	200	232	264
L4 [mm]	50	66	82	98	114	130	146	162	178	210	242	274

Pneumatic valves VUWG-S14, in-line valves G1/8


FESTO

Ordering data

Technical data – Manifold rails							
	Port	CRC	Material ²⁾	Operating pressure [bar]	Max. tightening torque for assembly [Nm]		
	1, 3, 5				Valve	H-rail	Wall
	G1/4	2 ¹⁾	Wrought aluminium alloy	–0.9 ... 10	0.65	1.5	3

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 2) Note on materials: RoHS-compliant.


Order code – Manifold rails							
VABM	–	L1	–	14	S	–	G14 –
Manifold assembly parts							Number of valve positions
Manifold rail VABM							2 to 10, 12, 14 and 16
Valve series							Ports 1, 3, 5
VUWG		L1					G14 G1/4
Valve width							
14 mm				14			
Manifold rail with ports 1, 3, 5							
For G1/8 in-line valves					S		

Ordering data – Manifold rail			
	Description	Part No.	Type
Manifold rail for in-line valves (manifold assembly)			
	For valve size G1/8	2 valve positions	566618 VABM-L1-14S-G14-2
		3 valve positions	566619 VABM-L1-14S-G14-3
		4 valve positions	566620 VABM-L1-14S-G14-4
		5 valve positions	566621 VABM-L1-14S-G14-5
		6 valve positions	566622 VABM-L1-14S-G14-6
		7 valve positions	566623 VABM-L1-14S-G14-7
		8 valve positions	566624 VABM-L1-14S-G14-8
		9 valve positions	566625 VABM-L1-14S-G14-9
		10 valve positions	566626 VABM-L1-14S-G14-10
		12 valve positions	566627 VABM-L1-14S-G14-12
		14 valve positions	566628 VABM-L1-14S-G14-14
		16 valve positions	566629 VABM-L1-14S-G14-16

Pneumatic valves VUWG-S14, in-line valves G1/8

FESTO

Ordering data

Ordering data – Accessories			
	Description	Part No.	Type
Blanking plate Technical data → Internet: vabb			
	For manifold rail for G1/8 in-line valves	Incl. screws and seal	569989 VABB-L1-14
Separator Technical data → Internet: vabd			
	For manifold rail for G1/8 in-line valves	Separator for pressure zones	569996 VABD-10-B
Supply plate Technical data → Internet: vabf			
	For manifold rail for G1/8 in-line valves	Incl. screws and seal	569993 VABF-L1-14-P3A4-G18
Seals for in-line valves Technical data → Internet: vabd			
	G1/8	Delivery unit: 10 sets (each with 2 screws and 1 seal)	566675 VABD-L1-14X-S-G18

Pneumatic valves VUWG-L18 and VUWG-S18, in-line valves G¹/₄

Technical data

Function

2x3/2C, 2x3/2U, 2x3/2H

5/2-way, single pilot

5/2-way, double pilot

5/3C, 5/3U, 5/3E

 Width 18 mm

 Flow rate
1,000 ... 1,380 l/min


General technical data												
Valve function	T32-A			T32-M			M52-R	B52	M52-M	P53		
Normal position	C ¹⁾	U ²⁾	H ⁴⁾	C ¹⁾	U ²⁾	H ⁴⁾	–	–	–	C ¹⁾	U ²⁾	E ³⁾
Pneumatic spring reset method	Yes			No			Yes ⁵⁾	–	No	No		
Mechanical spring reset method	No			Yes			Yes ⁵⁾	–	Yes	Yes		
Vacuum operation at port 1	No			Yes			No	Yes				
Vacuum operation at port 3/5	Yes											
Design	Piston spool valve											
Sealing principle	Soft											
Actuation type	Pneumatic											
Type of control	Direct											
Pilot air supply	External											
Exhaust function	With flow control											
Type of mounting	Optionally via through-holes ⁷⁾ or on manifold rail											
Mounting position	Any											
Standard nominal flow rate	[l/min]	1,000					1,300	1,380	1,300	1,200		
Switching time on/off	[ms]	12/36			17/25		16/40	–	12/59	17/69		
Changeover time	[ms]	–						12	–	34		
Width	[mm]	18										
Port	1, 2, 3, 4, 5	G¼										
	12, 14	M5										
Product weight	[g]	160					152	160	152			
Corrosion resistance class CRC ⁶⁾		2										

1) C = Normally closed

2) U=Normally open/mid-position pressurised

3) E = Normally exhausted

4) H=2x 3/2-way valve in one housing with 1x normally closed and 1x normally open

5) Combined reset method

6) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

7) If several valves are to be screwed together via the through-holes to form a block, a minimum gap of 0.3 mm must be ensured by placing spacer discs between them.

Pneumatic valves VUWG-L18 and VUWG-S18, in-line valves G¹/₄

FESTO

Technical data

Operating and environmental conditions						
Valve function	T32-A ²⁾	T32-M ³⁾	M52-R ⁴⁾	B52	M52-M ³⁾	P53
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]					
Note on operating/pilot medium	Lubricated operation possible (required during subsequent operation)					
Operating pressure [bar]	1.5 ... 10	-0.9 ... 10	2.5 ... 10	-0.9 ... 10	-0.9 ... 8	-0.9 ... 10
Pilot pressure ¹⁾ [bar]	1.5 ... 10	3 ... 10	2.5 ... 10	1.5 ... 10	3 ... 10	
Ambient temperature [°C]	-5 ... +60					
Temperature of medium [°C]	-5 ... +50					

1) Note operating pressure/pilot pressure graph → page 4

2) Pneumatic spring


3) Mechanical spring

4) Mixed, pneumatic/mechanical spring

Information on materials	
Housing	Wrought aluminium alloy
Seals	HNBR, NBR
Note on materials	RoHS-compliant

Dimensions Download CAD data → www.festo.com


2x3/2-way, 5/2-way and 5/3-way valve



Type	B1	D1	D2	D3	H1	H2	H3	H4	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10	L11
VUWG-L18-...	18.3	D ¹ / ₄	4.2	M5	43.1	40	37.8	6.4	115	96.1	86.4	105	52	34	31.3	23.8	9.7	21.1	14.3

Pneumatic valves VUWG-L18 and VUWG-S18, in-line valves G¹/₄

Technical data

Ordering data			
	Description	Part No.	Type
In-line valve G ¹ / ₄			
	2x3/2-way valve		
	Normally closed, external pilot air supply, reset method: pneumatic spring	574263	VUWG-L18-T32C-A-G14
	Normally open, external pilot air supply, reset method: pneumatic spring	574264	VUWG-L18-T32U-A-G14
	1x normally open, 1x normally closed, external pilot air supply, reset method: pneumatic spring	574265	VUWG-L18-T32H-A-G14
	Normally closed, external pilot air supply, reset method: mechanical spring	574266	VUWG-L18-T32C-M-G14
	Normally open, external pilot air supply, reset method: mechanical spring	574267	VUWG-L18-T32U-M-G14
	1x normally open, 1x normally closed, external pilot air supply, reset method: mechanical spring	574268	VUWG-L18-T32H-M-G14
	5/2-way valve, monostable		
	External pilot air supply, reset method: pneumatic/mechanical spring	574269	VUWG-L18-M52-R-G14
	External pilot air supply, reset method: mechanical spring	574270	VUWG-L18-M52-M-G14
	5/2-way valve, bistable		
	External pilot air supply	574271	VUWG-L18-B52-G14
	5/3-way valve		
	Mid-position closed, external pilot air supply	574272	VUWG-L18-P53C-G14
	Mid-position exhausted, external pilot air supply	574273	VUWG-L18-P53E-G14
	Mid-position pressurised, external pilot air supply	574274	VUWG-L18-P53U-G14

Pneumatic valves VUWG-L18 and VUWG-S18, in-line valves G1/4

Order code

FESTO

[illegible]

1) If Q... is chosen for the pneumatic connection, this also applies to the exhaust ports 3 and 5

2) Flow rate applies to 5/2-way individual valve

Pneumatic valves VUWG-S18, in-line valves G1¼

Manifold assembly


FESTO

In-line valves for
manifold assembly



Dimensions

Download CAD data → www.festo.com



1 Ports 1, 3 and 5: G3/8
2 Blanking plate
VABB-L1-18

3 Supply plate
VABF-L1-18-P3A4-G14
4 Double pilot pneumatic valve

5 Single pilot pneumatic valve

6 H-rail mounting (two M4x35 screws to DIN 912 are required)

Type	B1	B3	B4	B5	B6	B7	B8	B9	D1	H1	H2
VABM-L1-18S-G38	115	95.6	76.8	47.8	18.8	44.5	34.8	26	4.5	72.1	29


Type	H3	H4	H5	H6	L3	L4	L5	L6
VABM-L1-18S-G38	11.5	28.4	27.6	6.5	6	20.5	19	1

Valve positions	2	3	4	5	6	7	8	9	10	12	14	16
L1 [mm]	61	80	99	118	137	156	175	194	213	251	289	327
L2 [mm]	49	68	87	106	125	144	163	182	201	239	277	315

Pneumatic valves VUWG-S18, in-line valves G1/4


FESTO

Ordering data

Technical data – Manifold rails							
	Port	CRC	Material ²⁾	Operating pressure [bar]	Max. tightening torque for assembly [Nm]		
	1, 3, 5				Valve	H-rail	Wall
	G3/8	2 ¹⁾	Wrought aluminium alloy	-0.9 ... 10	0.65	1.5	3


- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
- 2) Note on materials: RoHS-compliant.

Order code – Manifold rails							
VABM	-	L1	-	18	S	-	G38
Manifold assembly parts							Number of valve positions
Manifold rail	VABM						2 to 10, 12, 14 and 16
Valve series							Ports 1, 3, 5
VUWG	L1						G38 G3/8
Valve width							
18 mm				18			
Manifold rail with ports 1, 3, 5							
For G1/8 in-line valves					S		

Ordering data – Manifold rail				
Description		Part No.	Type	
Manifold rail for in-line valve				
	For valve size G¼	2 valve positions	574455	VABM-L1-18S-G38-2
		3 valve positions	574456	VABM-L1-18S-G38-3
		4 valve positions	574457	VABM-L1-18S-G38-4
		5 valve positions	574458	VABM-L1-18S-G38-5
		6 valve positions	574459	VABM-L1-18S-G38-6
		7 valve positions	574460	VABM-L1-18S-G38-7
		8 valve positions	574461	VABM-L1-18S-G38-8
		9 valve positions	574462	VABM-L1-18S-G38-9
		10 valve positions	574463	VABM-L1-18S-G38-10
		12 valve positions	574464	VABM-L1-18S-G38-12
		14 valve positions	574465	VABM-L1-18S-G38-14
		16 valve positions	574466	VABM-L1-18S-G38-16

Pneumatic valves VUWG-S18, in-line valves G1/4

Ordering data

Ordering data – Accessories			
	Description	Part No.	Type
Blanking plate Technical data → Internet: vabb			
	For manifold rail for G1/4 in-line valves	Incl. screws and seal	574482 VABB-L1-18
Separator Technical data → Internet: vabd			
	For manifold rail for G1/4 in-line valves	Separator for pressure zones	574483 VABD-14-B
Supply plate Technical data → Internet: vabf			
	For manifold rail for G1/4 in-line valves	Incl. screws and seal	574481 VABF-L1-18-P3A4-G14
Seals for in-line valves Technical data → Internet: vabd			
	G1/4	Delivery unit: 10 sets (each with 2 screws and 1 seal)	574479 VABD-L1-18X-S-G14



Note

Connect supply plate at port 1 with compressed air. Reverse operation (pressure at port 3/5) is not permissible.

Pneumatic valves VUWG-B10A, sub-base valves

FESTO

Technical data

Function

5/2-way, single pilot
5/2-way, double pilot
5/3C, 5/3U, 5/3E

-  - Width 10 mm
-  - Flow rate
80 ... 100 l/min



General technical data						
Valve function		M52-R	B52	M52-M	P53	
Normal position		–	–	–	C ¹⁾	U ²⁾ E ³⁾
Pneumatic spring reset method		Yes ⁴⁾	–	No	No	
Mechanical spring reset method		Yes ⁴⁾	–	Yes	Yes	
Vacuum operation at port 1		No	Yes			
Vacuum operation at port 3/5		Yes				
Design		Piston spool valve				
Sealing principle		Soft				
Actuation type		Pneumatic				
Type of control		Direct				
Pilot air supply		External				
Exhaust function		With flow control				
Type of mounting		On manifold rail				
Mounting position		Any				
Standard nominal flow rate	[l/min]	100		80	90	
Switching time on/off	[ms]	5/11	–	5/16	7/19	
Changeover time	[ms]	–	5	–	9	
Width	[mm]	10				
Port	1, 3, 5	M7 in manifold rail				
	2, 4	M5 in manifold rail				
	12, 14	M5				
Product weight	[g]	37	40	34	40	
Corrosion resistance class CRC ⁵⁾		2				

1) C = Normally closed

2) U = Normally open/mid-position pressurised

3) E = Normally exhausted

4) Combined reset method

5) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Pneumatic valves VUWG-B10A, sub-base valves

FESTO

Technical data

Operating and environmental conditions				
Valve function	M52-R ³⁾	B52	M52-M ²⁾	P53
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]			
Note on operating/pilot medium	Lubricated operation possible (required during subsequent operation)			
Operating pressure [bar]	2.5 ... 10	-0.9 ... 10	-0.9 ... 8	-0.9 ... 10
Pilot pressure ¹⁾ [bar]	2.5 ... 10	1.5 ... 10	3 ... 10	
Ambient temperature [°C]	-5 ... +60			
Temperature of medium [°C]	-5 ... +50			


1) Note operating pressure/pilot pressure graph → page 4

2) Mechanical spring

3) Mixed, pneumatic/mechanical spring

Information on materials	
Housing	Anodised aluminium
Seals	HNBR, NBR
Note on materials	RoHS-compliant

Dimensions	Download CAD data → www.festo.com
5/2-way and 5/3-way valve	









Type	B1	L1
VUWG-B10A-...	10.3	59.9
VUWG-B10A-M52-...		49.9

Pneumatic valves VUWG-B10A, sub-base valves

Order code

FESTO

VUWG	-	B	10A	-		-		-	F
Valve design									Pneumatic connection
Sub-base, manifold valve incl. seal and screws									F In the manifold rail
									Reset method
Width									M Mechanical spring for M52
10 mm									R Pneu./mech. spring for M52
									- With B52 and P53
Valve functions									
									M52
									B52
									P53C
									P53U
									P53E

Pneumatic valves VUWG-B10A, sub-base valves

FESTO


Manifold assembly

Sub-base valve for
manifold assembly
M5 connection



Dimensions

Download CAD data → www.festo.com



- | | | |
|------------------------------------|--------------------------------|--|
| 1 Blanking plate VABB-L1-10A | 3 Double pilot pneumatic valve | 5 H-rail mounting (two M4x25 screws to DIN 912 are required) |
| 2 Supply plate VABF-L1-10A-P3A4-M5 | 4 Single pilot pneumatic valve | |

Type	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12
VABM-L1-10AW-M7	59.9	49.9	39.1	35	29.8	17.8	8.2	24	7.15	43.5	33.45	26.45

Type	H1	H2	H3	H4	H5	H6	H7	H8	H9	H10	D1	D2
VABM-L1-10AW-M7	50	12	9.1	6.3	11.6	3.6	13.1	4.2	16.2	6.8	M7	M5


Type	D3	D4	L3	L5	L6	L7	L8	L9	L10	L11
VABM-L1-10AW-M7	M5	∅ 4.5	7	12.5	10.5	10.2	10.5	16.5	14.7	11

Valve positions	2	3	4	5	6	7	8	9	10	12	14	16
L1 [mm]	42.5	53	63.5	74	84.5	96	106.5	116	126.5	147.5	168.5	189.5
L2 [mm]	28.5	39	49.5	60	70.5	81	91.5	102	112.5	133.5	154.5	175.5
L4 [mm]	35.5	46	56.5	67	77.5	89	99.5	109	119.5	140.5	161.5	182.5

Pneumatic valves VUWG-B10A, sub-base valves

FESTO

Ordering data

Technical data – Manifold rails ¹⁾									
	Port			CRC	Material ³⁾	Operating pressure [bar]	Max. tightening torque for assembly [Nm]		
	2, 4	1, 3, 5	12/14, 82/84				Valve	H-rail	Wall
	M5	M7	M5	2 ²⁾	Wrought aluminium alloy	–0.9 ... 10	0.45	1.5	1.5

1) Blanking plugs are included with the manifold rail.


2) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

3) Note on materials: RoHS-compliant.

Order code – Manifold rails M3

VABM	–	L1	–	10A	W	–	M7	–	
Manifold assembly parts							Number of valve positions		
Manifold rail		VABM					2 to 10, 12, 14 and 16		
Valve series							Ports 1, 3, 5		
VUWG		L1					M7	M7	
Valve width									
10 mm				10A					
Rail with ports 1, 2, 3, 4, 5, 12/14, 82/84									
Port 2 and 4 in M5					W				

Ordering data – Accessories				Part No.	Type
Blanking plate				Technical data → Internet: vabb	
	For manifold rail 10AW	Incl. screws and seal		569986	VABB-L1-10A
Separator				Technical data → Internet: vabd	
	For manifold rail 10AW	Separator for pressure zones		570872	VABD-4.2-B
Supply plate				Technical data → Internet: vabf	
	For manifold rail 10AW	Incl. screws and seal		569990	VABF-L1-10A-P3A4-M5
Seals				Technical data → Internet: vabd	
	For sub-base valves B10A	Delivery unit: 10 sets (each with 2 screws and 1 seal)		566671	VABD-L1-10AB-S-M3

Pneumatic valves VUWG-B10, sub-base valves

FESTO

Technical data

Function

2x3/2C, 2x3/2U, 2x3/2H

5/2-way, single pilot

5/2-way, double pilot

5/3C, 5/3U, 5/3E



Width 10 mm



Flow rate
120 ... 270 l/min



General technical data														
Valve function			T32-A			T32-M			M52-R	B52	M52-M	P53		
Normal position			C ¹⁾	U ²⁾	H ⁴⁾	C ¹⁾	U ²⁾	H ⁴⁾	–	–	–	C ¹⁾	U ²⁾	E ³⁾
Pneumatic spring reset method			Yes			No			Yes ⁵⁾	–	No	No		
Mechanical spring reset method			No			Yes			Yes ⁵⁾	–	Yes	Yes		
Vacuum operation at port 1			No			Yes			Yes ⁷⁾	Yes				
Vacuum operation at port 3/5			Yes											
Design			Piston spool valve											
Sealing principle			Soft											
Actuation type			Pneumatic											
Type of control			Direct											
Pilot air supply			External											
Exhaust function			With flow control											
Type of mounting			On manifold rail											
Mounting position			Any											
Standard nominal flow rate M5		[l/min]	150			130	120		210			180	200	
Standard nominal flow rate M7		[l/min]	160			140	130		270			230	250	
Switching time on/off		[ms]	4/9			6/7			6/12	–	7/16	8/25		
Changeover time		[ms]	–							5	–	11		
Width		[mm]	10											
Port		1, 3, 5	G1/8 in manifold rail											
		2, 4	M5/M7 in manifold rail											
		12, 14	M5											
Product weight		[g]	48			51		45	48	41	48			
Corrosion resistance class CRC ⁶⁾			2											

1) C = Normally closed

2) U=Normally open/mid-position pressurised

3) E = Normally exhausted

4) H=2x 3/2-way valve in one housing with 1x normally closed and 1x normally open

5) Combined reset method

6) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

7) Only with external pilot air supply

Pneumatic valves VUWG-B10, sub-base valves

FESTO

Technical data

Operating and environmental conditions						
Valve function	T32-A ²⁾	T32-M ³⁾	M52-R ⁴⁾	B52	M52-M ²⁾	P53
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]					
Note on operating/pilot medium	Lubricated operation possible (required during subsequent operation)					
Operating pressure [bar]	1.5 ... 10	-0.9 ... 10	2.5 ... 10	-0.9 ... 10	-0.9 ... 8	-0.9 ... 10
Pilot pressure ¹⁾ [bar]	1.5 ... 10	3 ... 10	2.5 ... 10	1.5 ... 10	3 ... 10	
Ambient temperature [°C]	-5 ... +60					
Temperature of medium [°C]	-5 ... +50					

1) Note operating pressure/pilot pressure graph → page 4

2) Pneumatic spring


3) Mechanical spring

4) Mixed, pneumatic/mechanical spring

Information on materials	
Housing	Wrought aluminium alloy
Seals	HNBR, NBR
Note on materials	RoHS-compliant

Dimensions Download CAD data → www.festo.com

2x3/2-way, 5/2-way and 5/3-way valve












Type	B1	H1	L1
VUWG-B10-...	10.3	32.5	72
VUWG-B10-M52-...			62

Pneumatic valves VUWG-B10, sub-base valves

FESTO

Order code

VUWG	-	B	10	-		-
Valve design						
Sub-base, manifold valve incl. seal and screws			B			
						
Width						
10 mm			10			
Valve functions						
			T32C			
			T32U			
			T32H			
			M52			
			B52			
			P53C			
			P53U			
			P53E			

	-	F
Pneumatic connection		
F	In the manifold rail	
Reset method		
A	Pneumatic spring for T32 and M52	
M	Mechanical spring for T32 and M52	
R	Pneu./mech. spring for M52	
-	With B52 and P53	

Pneumatic valves VUWG-B10, sub-base valves

FESTO


Manifold assembly

Sub-base valve for
manifold assembly
M5 or M7 connection



Dimensions

Download CAD data → www.festo.com



- | | | |
|--------------------------------------|---|--|
| 1 Supply plate
VABF-L1-10-P3A4-M5 | 3 Single pilot pneumatic valve,
VUWG-B10-M52 | 5 H-rail mounting (two M4x30
screws to DIN 912 are
required) |
| 2 Blanking plate
VABB-L1-10-W | 4 Double pilot pneumatic valve,
VUWG-B10 | |

Type	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12
VABM-L1-...G18	72	62	52.9	46.5	40.9	24.9	8.9	62	57.7	16.9	16	29.5

Type	B13	B14	D1	D2	D3	D4	H1	H2	H3	H4	H5	H6
VABM-L1-...G18	26.5	14.1	G $\frac{1}{8}$	M5	M5	4.5	56.4	15.7	12.2	7.9	23.9	10.8


Type	H7	H8	H9	H10	H11	L3	L4	L5	L6	L7	L8	L9	L15
VABM-L1-...G18	4	17.6	5.9	16.2	6.8	4	10.5	10.3	16	11	1	3	10

Valve positions	2	3	4	5	6	7	8	9	10	12	14	16	22
L1 [mm]	48.5	59	69.5	80	90.5	101	111.5	122	132.5	153.5	174.5	195.5	258.5
L2 [mm]	30.5	41	51.5	62	72.5	83	93.5	104	114.5	135.5	156.5	177.5	240.5

Pneumatic valves VUWG-B10, sub-base valves

FESTO

Ordering data

Technical data – Manifold rails ¹⁾									
	Port			CRC	Material ³⁾	Operating pressure [bar]	Max. tightening torque for assembly [Nm]		
	2, 4	1, 3, 5	12/14, 82/84				Valve	H-rail	Wall
	M5 or M7	G $\frac{1}{8}$	M5	2 ²⁾	Wrought aluminium alloy	-0.9 ... 10	0.45	1.5	3

1) Blanking plugs are included with the manifold rail.

2) Corrosion resistance class 2 according to Festo standard 940 070



Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

3) Note on materials: RoHS-compliant.

Order code – Manifold rails M5 and M7

VABM	-	L1	-	10	-	G18	-	
Manifold assembly parts								Number of valve positions
Manifold rail		VABM						2 to 10, 12, 14 and 16
Valve series								Ports 1, 3, 5
VUWG		L1				G18	G $\frac{1}{8}$	
Valve width								
10 mm				10				
Manifold rail with ports 1, 2, 3, 4, 5, 12/14, 82/84								
Port 2 and 4 in M5								W
Port 2 and 4 in M7								HW

Ordering data – Accessories

Ordering data – Accessories				
			Part No.	Type
Blanking plate			Technical data → Internet: vabb	
	For manifold rail 10W/10HW, sub-base valves	Incl. screws and seal	566495	VABB-L1-10-W
Separator			Technical data → Internet: vabd	
	For manifold rail 10W and 10HW, sub-base valves	Separator for pressure zones	569994	VABD-6-B
Supply plate			Technical data → Internet: vabf	
	For manifold rail 10W	Incl. screws and seal	569991	VABF-L1-10-P3A4-M5
	For manifold rail 10HW		569992	VABF-L1-10-P3A4-M7
Seals			Technical data → Internet: vabd	
	For sub-base valves B10	Delivery unit: 10 sets (each with 2 screws and 1 seal)	566674	VABD-L1-10B-S-M7

Pneumatic valves VUWG-B14, sub-base valves

FESTO

Technical data

Function

2x3/2C, 2x3/2U, 2x3/2H

5/2-way, single pilot

5/2-way, double pilot

5/3C, 5/3U, 5/3E

-  - Width 14 mm

-  - Flow rate
410 ... 580 l/min



General technical data												
Valve function		T32-A			T32-M			M52-A	B52	M52-M	P53	
Normal position		C ¹⁾	U ²⁾	H ⁴⁾	C ¹⁾	U ²⁾	H ⁴⁾	–	–	–	C ¹⁾	U ²⁾ E ³⁾
Pneumatic spring reset method		Yes			No			Yes	–	No	No	
Mechanical spring reset method		No			Yes			No	–	Yes	Yes	
Vacuum operation at port 1		No			Yes			No	Yes			
Vacuum operation at port 3/5		Yes										
Design		Piston spool valve										
Sealing principle		Soft										
Actuation type		Pneumatic										
Type of control		Direct										
Pilot air supply		External										
Exhaust function		With flow control										
Type of mounting		On manifold rail										
Mounting position		Any										
Standard nominal flow rate	[l/min]	540	510	540	430	410	580				540	510
Switching time on/off	[ms]	6/19			9/13		12/22	–		12/32	8/30	
Changeover time	[ms]	–						6		–		16
Width	[mm]	14										
Port	1, 3, 5	G¼ in manifold rail										
	2, 4	G⅛ in manifold rail										
	12, 14	M5										
Product weight	[g]	83			83		75	81				
Corrosion resistance class CRC ⁵⁾		2										

1) C = Normally closed

2) U=Normally open/mid-position pressurised

3) E = Normally exhausted

4) H=2x3/2-way valve in one housing with 1x normally closed and 1x normally open

5) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Pneumatic valves VUWG-B14, sub-base valves

FESTO

Technical data

Operating and environmental conditions						
Valve function	T32-A ²⁾	T32-M ³⁾	M52-A ²⁾	B52	M52-M ³⁾	P53
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]					
Note on operating/pilot medium	Lubricated operation possible (required during subsequent operation)					
Operating pressure [bar]	1.5 ... 10	-0.9 ... 10	2.5 ... 10	-0.9 ... 10	-0.9 ... 8	-0.9 ... 10
Pilot pressure ¹⁾ [bar]	1.5 ... 10	3 ... 10	2.5 ... 10	1.5 ... 10	3 ... 10	
Ambient temperature [°C]	-5 ... +60					
Temperature of medium [°C]	-5 ... +50					


1) Note operating pressure/pilot pressure graph → page 4

2) Pneumatic spring

3) Mechanical spring

Information on materials	
Housing	Wrought aluminium alloy
Seals	HNBR, NBR
Note on materials	RoHS-compliant

Dimensions	Download CAD data → www.festo.com
2x3/2-way, 5/2-way and 5/3-way valve	











Type	B1	H1	L1
VUWG-B14-...	14.4	34.8	92.6
VUWG-B14-M52-...			82.3

Pneumatic valves VUWG-B14, sub-base valves

Order code

FESTO

VUWG	-	B	14	-		-		-	F
Valve design									Pneumatic connection
Sub-base, manifold valve incl. seal and screws									F In the manifold rail
									Reset method
Width									A Pneumatic spring for T32 and M52
10 mm									M Mechanical spring for T32 and M52
									- With B52 and P53
Valve functions									
									T32C
									T32U
									T32H
									M52
									B52
									P53C
									P53U
									P53E

Pneumatic valves VUWG-B14, sub-base valves

FESTO


Manifold assembly

Sub-base valve for
manifold assembly
G $\frac{1}{8}$ connection



Dimensions

Download CAD data → www.festo.com



Type	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12
VUWG-B14 -...-F- ...	92.6	82.3	67.7	58.2	56.3	36.6	16.7	4.5	72.9	26.5	20	36.3

Type	B13	D1	D2	D3	D4	H1	H2	H3	H4	H5	H6	H7
VUWG-B14 -...-F- ...	36.3	G $\frac{1}{4}$	G $\frac{1}{8}$	M5	Ø 4.5	64.3	19.6	15.3	10.1	29.5	9.8	4.8


Type	H8	H9	H10	H11	L3	L5	L6	L7	L8	L9	L10	L11
VUWG-B14 -...-F- ...	22.1	7	15.4	6.8	6	1	16	14.4	11.3	18.5	16	14

Valve positions	2	3	4	5	6	7	8	9	10	12	14	16
L1 [mm]	56.3	72.3	88.3	104.3	120.3	136.3	152.3	168.3	184.3	216.3	248.3	280.3
L2 [mm]	40	56	72	88	104	120	136	152	168	200	232	264
L4 [mm]	54.3	70.3	86.3	102.3	118.3	134.3	150.3	166.3	182.3	214.3	246.6	278.3

Pneumatic valves VUWG-B14, sub-base valves

FESTO


Ordering data

Technical data – Manifold rails ¹⁾									
	Port			CRC	Material ³⁾	Operating pressure [bar]	Max. tightening torque for assembly [Nm]		
	2, 4	1, 3, 5	12/14, 82/84				Valve	H-rail	Wall
	G $\frac{1}{8}$	G $\frac{1}{4}$	M5	2 ²⁾	Wrought aluminium alloy	-0.9 ... 10	0.65	1.5	3

- 1) Blanking plugs are included with the manifold rail.
 2) Corrosion resistance class 2 according to Festo standard 940 070
 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.
 3) Note on materials: RoHS-compliant

Order code – Manifold rails G $\frac{1}{8}$

VABM	-	L1	-	14	W	-	G14	-	
Manifold assembly parts									Number of valve positions
Manifold rail		VABM							2 to 10, 12, 14 and 16
Valve series							Ports 1, 3, 5		
VUWG		L1					G14	G $\frac{1}{4}$	
Valve width									
14 mm				14					
Manifold rail with ports 1, 2, 3, 4, 5, 12/14, 82/84									
Ports 2 and 4 in G $\frac{1}{8}$					W				

Ordering data – Accessories				Part No.	Type
Blanking plate				Technical data → Internet: vabb	
	For manifold rail 14W, sub-base valves	Incl. screws and seal		569989	VABB-L1-14
Separator				Technical data → Internet: vabd	
	For manifold rail 14W, sub-base valves	Separator for pressure zones		569996	VABD-10-B
Supply plate				Technical data → Internet: vabf	
	For manifold rail 14W	Incl. screws and seal		569993	VABF-L1-14-P3A4-G18
Seals				Technical data → Internet: vabd	
	For sub-base valves B14	Delivery unit: 10 sets (each with 2 screws and 1 seal)		566676	VABD-L1-14B-S-G18

Pneumatic valves VUWG-B18, sub-base valves

Technical data

Function

2x3/2C, 2x3/2U, 2x3/2H

5/2-way, single pilot

5/2-way, double pilot

5/3C, 5/3U, 5/3E

 Width 18 mm

 Flow rate
900 ... 1,000 l/min


General technical data

Valve function		T32-A			T32-M			M52-R	B52	M52-M	P53			
Normal position		C ¹⁾	U ²⁾	H ⁴⁾	C ¹⁾	U ²⁾	H ⁴⁾	–	–	–	C ¹⁾	U ²⁾	E ³⁾	
Pneumatic spring reset method		Yes			No			Yes ⁵⁾	–	No	No			
Mechanical spring reset method		No			Yes			Yes ⁵⁾	–	Yes	Yes			
Vacuum operation at port 1		No			Yes			No	Yes					
Vacuum operation at port 3/5		Yes												
Design		Piston spool valve												
Sealing principle		Soft												
Actuation type		Pneumatic												
Type of control		Direct												
Pilot air supply		External												
Exhaust function		With flow control												
Type of mounting		On manifold rail												
Mounting position		Any												
Standard nominal flow rate		[l/min]	900					1,000				950		
Switching time on/off		[ms]	12/36			17/25			16/40	–	12/59	17/69		
Changeover time		[ms]	–						12		–	34		
Width		[mm]	18											
Port		1, 3, 5	G $\frac{3}{8}$ in manifold rail											
		2.4	G $\frac{1}{4}$ in manifold rail											
		12, 14	M5											
Product weight		[g]	83			83			75	81				
Corrosion resistance class CRC ⁶⁾		2												

1) C = Normally closed

2) U=Normally open/mid-position pressurised

3) E = Normally exhausted

4) H=2x 3/2-way valve in one housing with 1x normally closed and 1x normally open

5) Combined reset method

6) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Pneumatic valves VUWG-B18, sub-base valves

FESTO

Technical data

Operating and environmental conditions						
Valve function	T32-A ²⁾	T32-M ³⁾	M52-R ⁴⁾	B52	M52-M ³⁾	P53
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]					
Note on operating/pilot medium	Lubricated operation possible (required during subsequent operation)					
Operating pressure [bar]	1.5 ... 10	-0.9 ... 10	2.5 ... 10	-0.9 ... 10	-0.9 ... 8	-0.9 ... 10
Pilot pressure ¹⁾ [bar]	1.5 ... 10	3 ... 10	2.5 ... 10	1.5 ... 10	3 ... 10	
Ambient temperature [°C]	-5 ... +60					
Temperature of medium [°C]	-5 ... +50					

1) Note operating pressure/pilot pressure graph → page 4

2) Pneumatic spring


3) Mechanical spring

4) Mixed, pneumatic/mechanical spring

Information on materials	
Housing	Wrought aluminium alloy
Seals	HNBR, NBR
Note on materials	RoHS-compliant

Dimensions Download CAD data → www.festo.com









2x3/2-way, 5/2-way and 5/3-way valve



Type	B1	D3	H1	H2	H3	L1	L2	L3	L4	L9	L11
VUWG-B18-...	18.3	M5	43.1	40	37.8	115	96.1	86.4	105	9.7	14.3

Pneumatic valves VUWG-B18, sub-base valves

Order code

VUWG	-	B	18	-		-		F
Valve design								Pneumatic connection
Sub-base, manifold valve incl. seal and screws								F In the manifold rail
								Reset method
								A Pneumatic spring for T32 and M52
								M Mechanical spring for T32 and M52
								R Pneu./mech. spring for M52
								- With B52 and P53
Width								
18 mm								18
Valve functions								
								T32C
								T32U
								T32H
								M52
								B52
								P53C
								P53U
								P53E

Pneumatic valves VUWG-B18, sub-base valves

Manifold assembly


Sub-base valve for
manifold assembly
G $\frac{3}{8}$ connection

FESTO



Dimensions

Download CAD data → www.festo.com



1 Ports 1, 3 and 5: G $\frac{3}{8}$ (at both ends)

2 Ports 2 and 4: G $\frac{1}{4}$

3 Port 12/14 for external pilot air: M5

4 Port 82/84 for external pilot air: M5

5 Supply plate VABF-L1-18-P3A4-G14

6 Blanking plate VABB-L1-18

7 Double pilot pneumatic valve

8 Single pilot pneumatic valve

9 H-rail mounting (two M4x40 screws to DIN 912 are required for mounting)

Type	B1	B3	B4	B5	B6	B7	B8	B9	B10	B11	D1	H1
VUWG-B14 -...-F- ...	115	95.6	73.1	47.8	22.5	51.7	34.8	26	90.6	76.8	4.5	81.6


Type	H2	H3	H4	H5	H6	H7	H8	H9	H10	H11	H12	L3
VUWG-B14 -...-F- ...	38.5	23.8	28.4	27.6	19	12	12.1	6.1	29.1	8.8	6.5	6

Type	L4	L5	L6	L7	L8	L9	L10
VUWG-B14 -...-F- ...	23	19	20.8	19	15.6	8.5	1

Valve positions	2	3	4	5	6	7	8	9	10	12	14	16
L1 [mm]	63.5	82.5	101.5	120.5	139.5	158.5	177.5	196.5	215.5	253.5	291.5	329.5
L2 [mm]	49	68	87	106	125	144	163	182	201	239	277	315

Pneumatic valves VUWG-B18, sub-base valves

Ordering data

Technical data – Manifold rails ¹⁾									
	Port			CRC	Material ³⁾	Operating pressure [bar]	Max. tightening torque for assembly [Nm]		
	2, 4	1, 3, 5	12/14, 82/84				Valve	H-rail	Wall
	G $\frac{1}{4}$	G $\frac{3}{8}$	M5	2 ²⁾	Wrought aluminium alloy	–0.9 ... 10	0.65	1.5	3

1) Blanking plugs are included with the manifold rail.


2) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

3) Note on materials: RoHS-compliant.

Order code – Manifold rails G $\frac{1}{4}$

VABM	–	L1	–	18	W	–	G38	–	
Manifold assembly parts									Number of valve positions
Manifold rail VABM									2 to 10, 12, 14 and 16
Valve series							Ports 1, 3, 5		
VUWG		L1					G38	G $\frac{3}{8}$	
Valve width									
18 mm					18				
Manifold rail with ports 1, 2, 3, 4, 5, 12/14, 82/84									
Ports 2 and 4 in G $\frac{1}{4}$									W

Ordering data – Accessories				Part No.	Type
Blanking plate				Technical data → Internet: vabb	
	For manifold rail 18W, sub-base valves	Incl. screws and seal		574482	VABB-L1-18
Separator				Technical data → Internet: vabd	
	For manifold rail 18W, sub-base valves	Separator for pressure zones		574483	VABD-14-B
Supply plate				Technical data → Internet: vabf	
	For manifold rail 18W	Incl. screws and seal		574481	VABF-L1-18-P3A4-G14
Seals				Technical data → Internet: vabd	
	For sub-base valves B18	Delivery unit: 10 sets (each with 2 screws and 1 seal)		574480	VABD-L1-18B-S-G14

Pneumatic valves VUWG

Accessories


FESTO

Ordering data				
	Description		Part No.	Type
Pneumatic silencer			Technical data → Internet: u	
	For thread M5	1 piece	165003	UC-M5
	For thread M7		161418	UC-M7
	For thread G1/8	50 pieces	534222	U-1/8-50
		1 piece	161419	UC-1/8
	For thread G1/4	20 pieces	534220	UC-1/4-20
			534223	U-1/4-20
Fittings			Technical data → Internet: qs	
	For tubing Ø 3 mm	10 pieces	133003	QSM-M5-3-I-R
	For tubing Ø 4 mm		133004	QSM-M5-4-I-R
	For tubing Ø 6 mm		133005	QSM-M5-6-I-R
	For tubing Ø 6 mm		133007	QSM-M7-6-I-R
	For tubing Ø 3 mm		153313	QSM-M5-3-I
	For tubing Ø 4 mm		153315	QSM-M5-4-I
	For tubing Ø 4 mm		153319	QSM-M7-4-I
	For tubing Ø 4 mm	10 pieces	186106	QS-G1/8-4-I
	For tubing Ø 6 mm		186107	QS-G1/8-6-I
	For tubing Ø 8 mm		186109	QS-G1/8-8-I
	For tubing Ø 8 mm	20 pieces	130995	QS-B-1/4-8-I-20
	For tubing Ø 10 mm		132152	QS-B-1/4-10-I-20
	For tubing Ø 12 mm		132153	QS-B-1/4-12-I-20
	For tubing Ø 10 mm		132151	QS-B-1/8-10-I-20
	For tubing Ø 6 mm	10 pieces	186117	QSL-G1/8-6
	For tubing Ø 8 mm		186119	QSL-G1/8-8
	For tubing Ø 8 mm	20 pieces	130931	QSL-B-1/4-8-20
	For tubing Ø 10 mm		132127	QSL-B-1/4-10-20
	For tubing Ø 12 mm		132128	QSL-B-1/4-12-20
	For tubing Ø 10 mm		132126	QSL-B-1/8-10-20
	For tubing Ø 6 mm	10 pieces	186128	QSL-G1/8-6
	For tubing Ø 8 mm		186130	QSL-G1/8-8
	For tubing Ø 6 mm	20 pieces	132111	QSM-B-1/8-6-20
	For tubing Ø 3 mm	10 pieces	153331	QSM-M5-3
	For tubing Ø 4 mm		153333	QSM-M5-4
	For tubing Ø 4 mm		186352	QSM-M7-4
	For tubing Ø 3 mm		130838	QSM-M5-3
	For tubing Ø 4 mm		153339	QSM-M5-4
	For tubing Ø 4 mm		186354	QSM-M7-4
Blanking plug			Technical data → Internet: b	
	For thread M5	10 pieces	174308	B-M5-B
	For thread M7		174309	B-M7
	For thread G1/8		3568	B-1/8
	For thread G1/4		3569	B-1/4
Compact blanking plug, for valve			Technical data → Internet: npqh	
	For sealing a connection (valve requires a blanking plug with a low screw-in depth)	For valve size 14 (G1/8), 10 pieces	578406	NPQH-BK-G18-P10
		For valve size 18 (G1/4), 10 pieces	578407	NPQH-BK-G14-P10

Pneumatic valves VUWG

Accessories

FESTO

Ordering data						
	Description				Part No.	Type
H-rail						
Technical data → Internet: nrh						
	To EN 60715, 35 x 7.5 (WxH)	2 m	35430	NRH-35-2000		
H-rail mounting						
Technical data → Internet: vame						
	–	2 pieces	569998	VAME-T-M4		
Flow control valve						
	For M5 valves, for setting the flow rate during pressurisation and exhausting (10 pieces)	Flow rate: 9.6 l/min	b value: 0.5	C value: 0.04	8025709	VFFG-T-M5-5
		Flow rate: 14.6 l/min	b value: 0.5	C value: 0.05	8025710	VFFG-T-M5-6
		Flow rate: 19.1 l/min	b value: 0.5	C value: 0.07	8025711	VFFG-T-M5-7
		Flow rate: 26.1 l/min	b value: 0.5	C value: 0.10	8025712	VFFG-T-M5-8
		Flow rate: 40.8 l/min	b value: 0.5	C value: 0.14	8025713	VFFG-T-M5-10
		Flow rate: 45.4 l/min	b value: 0.5	C value: 0.16	8025714	VFFG-T-M5-12
		Flow rate: 67.4 l/min	b value: 0.5	C value: 0.25	8025715	VFFG-T-M5-15