


Parallel kits EAMM-U

FESTO



Festo core product range
Covers 80% of your automation tasks

Worldwide:

Always in stock

Superb:

Festo quality at an attractive price

Easy:

Reduces procurement and storing complexity



Ready for dispatch from the Festo factory in 24 hours
Held in stock in 13 service centres worldwide
More than 2200 products



Ready for dispatch in 5 days maximum from stock
Assembled for you in 4 service centres worldwide
Up to 6×10^{12} variants per product series

Look for the star!

Parallel kits EAMM-U

Key features



At a glance			
	For axis	Description	→ Page
Parallel kits EAMM-U-...-D			
	• Electric cylinder ESBF • Mini slide EGSL	• The kit can be mounted in all directions • Transmission ratio: $i = 1$ • Optionally with degree of protection IP65 • Third-party motors can be connected. You can find out which motors are permitted from your local Festo contact or from → www.festo.com/sp/eamm	4
Parallel kits EAMM-U-...-S			
	• Spindle axis ELGA-BS • Spindle axis EGC-BS • Spindle axis EGC-HD-BS	• The kit can be mounted in all directions • Transmission ratio: $i = 1$ • A counter bearing EAMG and a clamping sleeve EAMH-...-P with integrated trunnion are included in the scope of delivery of the parallel kit to provide support for the axis shaft • Third-party motors can be connected. You can find out which motors are permitted from your local Festo contact or from → www.festo.com/sp/eamm	4
Parallel kits EAMM-U-...-V/T			
	• Mini slide EGSC-BS • Spindle axis ELGC-BS	• The kit can be mounted in all directions • Transmission ratio: $i = 1$ • Third-party motors can be connected. You can find out which motors are permitted from your local Festo contact or from → www.festo.com/sp/eamm	25
Parallel kits EAMM-U-E/-D			
	• Spindle axis DGE-SP • Mini slide EGSL	• The kit can be mounted in all directions • The kit EGSL can only be mounted at the side and underneath • Transmission ratio: $i = 1$	30

- Note

Depending on the combination of motor and drive, it may not be possible to reach the maximum feed force of the drive in certain circumstances.
When using parallel kits, the no-load driving torque of the respective kit must be taken into consideration.

PositioningDrives
Engineering software
www.festo.com

Parallel kits EAMM-U

Key features

FESTO

Accessories for parallel kit EAMM-U-...-D/S

Clamping element EADT

→ Page 21



For setting the toothed belt pretension with EAMM-U-110 and EAMM-U-145. The motor is pushed away from the axis mechanism by rotating the clamping element secured in a hole in the housing (the motor can be moved in a slot for this purpose). This enables high toothed-belt pretension forces to be generated with low torques at the clamping element.

Counter bearing EAMG

→ Page 21



A counter bearing EAMG reduces the load on the axis or motor bearings to improve the service life under high loads. A clamping sleeve EAMH-...-P is additionally required for each counter bearing.

Clamping sleeve EAMH-...-P

→ Page 22



To retrofit the counter bearing, the clamping sleeve without trunnion, included as standard in the parallel kit, must be replaced by the spring pin EAMH-...-P with integrated trunnion.

Clamping sleeve EAMH-...


→ Page 23



Clamping sleeves for adapting third-party motors with deviating shaft diameters to the parallel kits.

Seal set EADS-F-...

→ Page 24




Spare part for sealed parallel kit EAMM-U-...-S1, between motor and kit.

Parallel kits EAMM-U-...-D/S



Type codes



EAMM	-	U	-	50	-	D32	-	40A	-	78	-	
------	---	---	---	----	---	-----	---	-----	---	----	---	--


Type	
EAMM	Kit
Motor placement	
U	Parallel
Size	
Axis mechanism interface	
D32	ESBF-32, EGSL-45
D40	ESBF-40, EGSL-55
D50	ESBF-50
D60	EGSL-75, ESBF-63
D80	ESBF-80
D100	ESBF-100
S38	ELGA-BS-70, EGC-70-BS, EGC-HD-125-BS
S48	ELGA-BS-80, EGC-80-BS, EGC-HD-160-BS
S62	ELGA-BS-120, EGC-120-BS, EGC-HD-220-BS
S95	ELGA-BS-150, EGC-185-BS
Motor interface	
40P	Servo motor EMME-AS-40
60P	Servo motor EMMT-AS-60, EMME-AS-60
80P	Servo motor EMME-AS-80
40A	Servo motor EMMS-AS-40
55A	Servo motor EMMS-AS-55
70A	Servo motor EMMS-AS-70
100A	Servo motor EMME-AS-100, EMMS-AS-100
140A	Servo motor EMMS-AS-140
42A	Stepper motor EMMS-ST-42
57A	Stepper motor EMMS-ST-57
87A	Stepper motor EMMS-ST-87
67A	Integrated drive EMCA-EC-67
40G	Gear unit EMGA-40
60G	Gear unit EMGA-60-P-...-SAS/SST
60H	Gear unit EMGA-60-P-...-EAS, EMGC-60-P
80G	Gear unit EMGA-80
120G	Gear unit EMGA-120
Centre distance	
Special design	
S1	Degree of protection IP65

Parallel kits EAMM-U-...-D/S

Product range overview

FESTO

Permissible axis/motor combinations with electric cylinder ESBF



- The kit can be mounted in all directions
- Optionally with degree of protection IP65
- Third-party motors can be connected. You can find out which motors are permitted from your local Festo contact or from
→ www.festo.com/sp/eamm

Motor / gear unit ²⁾	Parallel kit	
Type	Part No.	Type
ESBF-32		
With servo motor		
EMME-AS-40-...	★ 2153283	EAMM-U-50-D32-40P-78
	2154009	EAMM-U-50-D32-40P-78-S1 ¹⁾
EMMS-AS-40-...	1201591	EAMM-U-50-D32-40A-78
	1202302	EAMM-U-50-D32-40A-78-S1 ¹⁾
EMMS-AS-55-...	1210126	EAMM-U-60-D32-55A-91
	1210450	EAMM-U-60-D32-55A-91-S1 ¹⁾
EMMT-AS-60-...	★ 2619586	EAMM-U-70-D32-60P-96
	2619688	EAMM-U-70-D32-60P-96-S1 ¹⁾
EMME-AS-60-...	★ 2619586	EAMM-U-70-D32-60P-96
	2619688	EAMM-U-70-D32-60P-96-S1 ¹⁾
EMMS-AS-70-...	2755565	EAMM-U-70-D32-70A-96
	2781711	EAMM-U-70-D32-70A-96-S1 ¹⁾
With stepper motor		
EMMS-ST-42-...	★ 1201607	EAMM-U-50-D32-42A-78
	1202312	EAMM-U-50-D32-42A-78-S1 ¹⁾
EMMS-ST-57-...	★ 1210419	EAMM-U-60-D32-57A-91
	1210453	EAMM-U-60-D32-57A-91-S1 ¹⁾
With gear unit		
EMGA-40-P-...	1577358	EAMM-U-60-D32-40G-91
EMGC-40-P-...	1577346	EAMM-U-60-D32-40G-91-S1 ¹⁾
EMGA-60-P-...-EAS, EMGC-60-P-... ³⁾	2778393	EAMM-U-70-D32-60H-96
	2781450	EAMM-U-70-D32-60H-96-S1 ¹⁾
EMGA-60-P-...-SAS/ SST ³⁾	2748181	EAMM-U-70-D32-60G-96
	2778302	EAMM-U-70-D32-60G-96-S1 ¹⁾
With integrated drive		
EMCA-EC-67-...	1577063	EAMM-U-60-D32-67A-91
	1529422	EAMM-U-60-D32-67A-91-S1

- - Note

The seal on EAMM-U-...-S1 reduces the dissipation of heat between the motor and flange. Note derating of motor.

Motor / gear unit ²⁾	Parallel kit	
Type	Part No.	Type
ESBF-40		
With servo motor		
EMMS-AS-55-...	1210438	EAMM-U-60-D40-55A-91
	1210458	EAMM-U-60-D40-55A-91-S1 ¹⁾
EMMT-AS-60-...	★ 2617488	EAMM-U-70-D40-60P-96
	2546123	EAMM-U-70-D40-60P-96-S1 ¹⁾
EMME-AS-60-...	★ 2617488	EAMM-U-70-D40-60P-96
	2546123	EAMM-U-70-D40-60P-96-S1 ¹⁾
EMMS-AS-70-...	2786204	EAMM-U-70-D40-70A-96
	2786316	EAMM-U-70-D40-70A-96-S1 ¹⁾
EMMS-AS-70-...	1212826	EAMM-U-86-D40-70A-102
	1212854	EAMM-U-86-D40-70A-102-S1 ¹⁾
EMME-AS-80-...	★ 2802441	EAMM-U-86-D40-80P-102
	2802656	EAMM-U-86-D40-80P-102-S1 ¹⁾
With stepper motor		
EMMS-ST-57-...	★ 1210442	EAMM-U-60-D40-57A-91
	1210462	EAMM-U-60-D40-57A-91-S1 ¹⁾
EMMS-ST-87-...	★ 1215802	EAMM-U-86-D40-87A-102
	1215814	EAMM-U-86-D40-87A-102-S1 ¹⁾
With gear unit		
EMGA-40-P-...	1577165	EAMM-U-60-D40-40G-91
EMGC-40-P-...	1435968	EAMM-U-60-D40-40G-91-S1 ¹⁾
EMGA-60-P-...-EAS, EMGC-60-P-... ³⁾	2786101	EAMM-U-70-D40-60H-96
	2786137	EAMM-U-70-D40-60H-96-S1 ¹⁾
EMGA-60-P-...-SAS/ SST ³⁾	2785471	EAMM-U-70-D40-60G-96
	2785542	EAMM-U-70-D40-60G-96-S1 ¹⁾
EMGA-60-P-...-EAS, EMGC-60-P-... ³⁾	1586496	EAMM-U-86-D40-60H-102
	1586372	EAMM-U-86-D40-60H-102-S1 ¹⁾
EMGA-60-P-...-SAS/ SST ³⁾	1586445	EAMM-U-86-D40-60G-102
	1586429	EAMM-U-86-D40-60G-102-S1 ¹⁾
With integrated drive		
EMCA-EC-67-...	1577083	EAMM-U-60-D40-67A-91
	1435249	EAMM-U-60-D40-67A-91-S1

1) With degree of protection IP65

2) The input torque must not exceed the maximum permissible transferable torque of the parallel kit.

3) Gear unit output shaft diameter: EMGA-60-P-...-SAS/SST11 mm; EMGA-60-P-...-EAS, EMGC-60-P14 mm.

Festo core product range

★ Generally ready for shipping ex works in 24 hours


☆ Generally ready for shipping ex works in 5 days

Parallel kits EAMM-U-...-D/S

Product range overview

FESTO

Permissible axis/motor combinations with electric cylinder ESBF



- The kit can be mounted in all directions
- Optionally with degree of protection IP65
- Third-party motors can be connected. You can find out which motors are permitted from your local Festo contact or from
→ www.festo.com/sp/eamm

Motor / gear unit ²⁾	Parallel kit	
Type	Part No.	Type
ESBF-50		
With servo motor		
EMMS-AS-70-...	2786899	EAMM-U-70-D50-70A-96
	2756078	EAMM-U-70-D50-70A-96-S1 ¹⁾
EMME-AS-80-...	★ 2803053	EAMM-U-86-D50-80P-102
	2803073	EAMM-U-86-D50-80P-102-S1 ¹⁾
EMME-AS-100-...	2799424	EAMM-U-110-D50-100A-120
	2799488	EAMM-U-110-D50-100A-120-S1 ¹⁾
EMMS-AS-100-...	★ 2799424	EAMM-U-110-D50-100A-120
	2799488	EAMM-U-110-D50-100A-120-S1 ¹⁾
With stepper motor		
EMMS-ST-87-...	★ 2802708	EAMM-U-86-D50-87A-102
	2802742	EAMM-U-86-D50-87A-102-S1 ¹⁾
With gear unit		
EMGA-60-P-...-EAS, EMGC-60-P-... ³⁾	2803326	EAMM-U-86-D50-60H-102
	2803325	EAMM-U-86-D50-60H-102-S1 ¹⁾
EMGA-60-P-...-SAS/ SST ³⁾	2803125	EAMM-U-86-D50-60G-102
	2803197	EAMM-U-86-D50-60G-102-S1 ¹⁾
EMGA-60-P-...-EAS, EMGC-60-P-... ³⁾	2798760	EAMM-U-110-D50-60H-120
	2799150	EAMM-U-110-D50-60H-120-S1 ¹⁾
EMGA-60-P-...-SAS/ SST ³⁾	2797368	EAMM-U-110-D50-60G-120
	2798665	EAMM-U-110-D50-60G-120-S1 ¹⁾
EMGA-80-P-...	2799196	EAMM-U-110-D50-80G-120
	2799281	EAMM-U-110-D50-80G-120-S1 ¹⁾
ESBF-63		
With servo motor		
EMMS-AS-70-...	1212477	EAMM-U-86-D60-70A-102
	1212835	EAMM-U-86-D60-70A-102-S1 ¹⁾
EMME-AS-80-...	★ 2155875	EAMM-U-86-D60-80P-102
	2156527	EAMM-U-86-D60-80P-102-S1 ¹⁾
EMME-AS-100-...	★ 1202436	EAMM-U-110-D60-100A-120 ¹⁾
	1203112	EAMM-U-110-D60-100A-120-S1 ¹⁾
EMMS-AS-100-...	★ 1202436	EAMM-U-110-D60-100A-120 ¹⁾
	1203112	EAMM-U-110-D60-100A-120-S1 ¹⁾
With stepper motor		
EMMS-ST-87-...	★ 1215784	EAMM-U-86-D60-87A-102
	1215810	EAMM-U-86-D60-87A-102-S1 ¹⁾

Motor / gear unit ²⁾	Parallel kit	
Type	Part No.	Type
ESBF-63		
With gear unit		
EMGA-60-P-...-SAS/ SST ³⁾	1586347	EAMM-U-86-D60-60G-102
	1437163	EAMM-U-86-D60-60G-102-S1 ¹⁾
EMGA-60-P-...-EAS, EMGC-60-P-... ³⁾	1586276	EAMM-U-86-D60-60H-102
	1530837	EAMM-U-86-D60-60H-102-S1 ¹⁾
EMGA-60-P-...-SAS/ SST ³⁾	1543240	EAMM-U-110-D60-60G-120
	1436183	EAMM-U-110-D60-60G-120-S1 ¹⁾
EMGA-60-P-...-EAS, EMGC-60-P-... ³⁾	1542264	EAMM-U-110-D60-60H-120
	1530621	EAMM-U-110-D60-60H-120-S1 ¹⁾
EMGA-80-P-...	1532949	EAMM-U-110-D60-80G-120
	1530875	EAMM-U-110-D60-80G-120-S1 ¹⁾
ESBF-80		
With servo motor		
EMME-AS-100-...	1465438	EAMM-U-110-D80-100A-120
	1433650	EAMM-U-110-D80-100A-120-S1 ¹⁾
EMMS-AS-100-...	1465438	EAMM-U-110-D80-100A-120
	1433650	EAMM-U-110-D80-100A-120-S1 ¹⁾
EMMS-AS-140-...	1465530	EAMM-U-145-D80-140A-188
	1433709	EAMM-U-145-D80-140A-188-S1 ¹⁾
With gear unit		
EMGA-80-P-...	1589614	EAMM-U-110-D80-80G-120
	1589706	EAMM-U-110-D80-80G-120-S1 ¹⁾
ESBF-100		
With servo motor		
EMMS-AS-140-...	1465541	EAMM-U-145-D100-140A-188
	1433852	EAMM-U-145-D100-140A-188-S1 ¹⁾
With gear unit		
EMGA-120-P-... -	2803620	EAMM-U-145-D100-120G-188
	2803622	EAMM-U-145-D100-120G-188-S1 ¹⁾

- 1) With degree of protection IP65
- 2) The input torque must not exceed the maximum permissible transferable torque of the parallel kit.
- 3) Gear unit output shaft diameter: EMGA-60-P-...-SAS/-SST11 mm; EMGA-60-P-...-EAS, EMGC-60-P14 mm.

- Note

Clamping element EADT for adjusting the toothed belt pretension with EAMM-U-110 and EAMM-U-145 → Page 21

The seal on EAMM-U-...-S1 reduces the dissipation of heat between the motor and flange. Note derating of motor.

Festo core product range


- ★ Generally ready for shipping ex works in 24 hours
- ★ Generally ready for shipping ex works in 5 days

Parallel kits EAMM-U-...-D/S

Product range overview

FESTO

Permissible axis/motor combinations with mini slide EGSL



- The kit can be mounted in all directions
- Third-party motors can be connected. You can find out which motors are permitted from your local Festo contact or from
→ www.festo.com/sp/eamm

Motor / gear unit ¹⁾	Parallel kit	
Type	Part No.	Type
EGSL-45		
With servo motor		
EMME-AS-40-...	★ 2153283	EAMM-U-50-D32-40P-78
EMMS-AS-40-...	1201591	EAMM-U-50-D32-40A-78
EMMS-AS-55-...	1210126	EAMM-U-60-D32-55A-91
EMMT-AS-60-...	★ 2619586	EAMM-U-70-D32-60P-96
EMME-AS-60-...	★ 2619586	EAMM-U-70-D32-60P-96
With stepper motor		
EMMS-ST-42-...	★ 1201607	EAMM-U-50-D32-42A-78
EMMS-ST-57-...	★ 1210419	EAMM-U-60-D32-57A-91
With integrated drive		
EMCA-EC-67-...	1577063	EAMM-U-60-D32-67A-91
With gear unit		
EMGA-40-P-...	1577358	EAMM-U-60-D32-40G-91
EMGC-40-P-...		
EMGA-60-P-...-SAS/ SST ²⁾	2748181	EAMM-U-70-D32-60G-96
EMGA-60-P-...-EAS, EMGC-60-P-... ²⁾	2778393	EAMM-U-70-D32-60H-96
EGSL-55		
With servo motor		
EMMS-AS-55-...	1210438	EAMM-U-60-D40-55A-91
EMMT-AS-60-...	★ 2617488	EAMM-U-70-D40-60P-96
EMME-AS-60-...	★ 2617488	EAMM-U-70-D40-60P-96
EMMS-AS-70-...	2786204	EAMM-U-70-D40-70A-96
EMMS-AS-70-...	1212826	EAMM-U-86-D40-70A-102
With stepper motor		
EMMS-ST-57-...	★ 1210442	EAMM-U-60-D40-57A-91
EMMS-ST-87-...	★ 1215802	EAMM-U-86-D40-87A-102
With integrated drive		
EMCA-EC-67-...	1577083	EAMM-U-60-D40-67A-91

Motor / gear unit ¹⁾	Parallel kit	
Type	Part No.	Type
EGSL-55		
With gear unit		
EMGA-40-P-...	1577165	EAMM-U-60-D40-40G-91
EMGC-40-P-...		
EMGA-60-P-...-SAS/ SST ²⁾	2785471	EAMM-U-70-D40-60G-96
EMGA-60-P-...-EAS, EMGC-60-P-... ²⁾	2786101	EAMM-U-70-D40-60H-96
EMGA-60-P-...-SAS/ SST ²⁾	1586445	EAMM-U-86-D40-60G-102
EMGA-60-P-...-EAS, EMGC-60-P-... ²⁾	1586496	EAMM-U-86-D40-60H-102
EGSL-75		
With servo motor		
EMMS-AS-70-...	1212477	EAMM-U-86-D60-70A-102
EMME-AS-80-...	★ 2155875	EAMM-U-86-D60-80P-102
With stepper motor		
EMMS-ST-87-...	★ 1215784	EAMM-U-86-D60-87A-102
With gear unit		
EMGA-60-P-...-SAS/ SST ²⁾	1536988	EAMM-U-86-D60-60G-102
EMGA-60-P-...-EAS, EMGC-60-P-... ²⁾	1536988	EAMM-U-86-D60-60H-102
EMGA-60-P-...-SAS/ SST ²⁾	1543240	EAMM-U-110-D60-60G-120
EMGA-60-P-...-EAS, EMGC-60-P-... ²⁾	1542264	EAMM-U-110-D60-60H-120
EMGA-80-P-...	1532949	EAMM-U-110-D60-80G-120

- 1) The input torque must not exceed the maximum permissible transferable torque of the parallel kit.
2) Gear unit output shaft diameter: EMGA-60-P-...-SAS/-SST11 mm; EMGA-60-P-...-EAS, EMGC-60-P14 mm.

-  - Note

Clamping element EADT for adjusting the toothed belt pretension with EAMM-U-110 and EAMM-U-145 → Page 21

Festo core product range


- ★ Generally ready for shipping ex works in 24 hours
- ★ Generally ready for shipping ex works in 5 days

Parallel kits EAMM-U-...-D/S

Product range overview

FESTO

Permissible axis/motor combinations with spindle axis ELGA-BS



- The kit can be mounted in all directions
- A counter bearing EAMG and a clamping sleeve EAMH-...-P with integrated trunnion are included in the scope of delivery of the parallel kit to provide support for the axis shaft
- Third-party motors can be connected. You can find out which motors are permitted from your local Festo contact or from
→ www.festo.com/sp/eamm

Motor / gear unit ¹⁾	Parallel kit	
Type	Part No.	Type
ELGA-BS-70		
With servo motor		
EMME-AS-40-...	★ 2155239	EAMM-U-50-S38-40P-78
EMMS-AS-40-...	1217708	EAMM-U-50-S38-40A-78
EMMS-AS-55-...	1218538	EAMM-U-60-S38-55A-91
With stepper motor		
EMMS-ST-42-...	★ 1217945	EAMM-U-50-S38-42A-78
EMMS-ST-57-...	★ 1218568	EAMM-U-60-S38-57A-91
With gear unit		
EMGA-40-P-...	2283732	EAMM-U-60-S38-40G-91
EMGC-40-P-...	2283732	EAMM-U-60-S38-40G-91
ELGA-BS-80		
With servo motor		
EMMS-AS-55-...	1219370	EAMM-U-60-S48-55A-91
EMMT-AS-60-...	★ 2629253	EAMM-U-70-S48-60P-96
EMME-AS-60-...	★ 2629253	EAMM-U-70-S48-60P-96
EMMS-AS-70-...	2787320	EAMM-U-70-S48-70A-96
EMMS-AS-70-...	1217689	EAMM-U-86-S48-70A-102
With stepper motor		
EMMS-ST-57-...	1219379	EAMM-U-60-S48-57A-91
EMMS-ST-87-...	1217604	EAMM-U-86-S48-87A-177
With gear unit		
EMGA-40-P-...	2283760	EAMM-U-60-S48-40G-91
EMGC-40-P-...	2283760	EAMM-U-60-S48-40G-91
EMGA-60-P-...-SAS/ SST ²⁾	2283760	EAMM-U-70-S48-60G-96
EMGA-60-P-...-EAS, EMGC-60-P-... ²⁾	2801715	EAMM-U-70-S48-60H-96
EMGA-60-P-...-SAS/ SST ²⁾	1587251	EAMM-U-86-S48-60G-102
EMGA-60-P-...-EAS, EMGC-60-P-... ²⁾	1587338	EAMM-U-86-S48-60H-102

Motor / gear unit ¹⁾	Parallel kit	
Type	Part No.	Type
ELGA-BS-120		
With servo motor		
EMMS-AS-70-...	1217543	EAMM-U-86-S62-70A-177
EMME-AS-80-...	★ 2157004	EAMM-U-86-S62-80P-177
EMME-AS-100-...	★ 1217381	EAMM-U-110-S62-100A-207
EMMS-AS-100-...	★ 1217381	EAMM-U-110-S62-100A-207
EMMS-AS-140-...	★ 1219440	EAMM-U-145-S62-140A-288
With stepper motor		
EMMS-ST-87-...	★ 1217373	EAMM-U-86-S62-87A-177
With gear unit		
EMGA-60-P-...-SAS/ SST ²⁾	1587411	EAMM-U-86-S62-60G-177
EMGA-60-P-...-EAS, EMGC-60-P-... ²⁾	1587453	EAMM-U-86-S62-60H-177
ELGA-BS-150		
With servo motor		
EMME-AS-100-...	1220656	EAMM-U-110-S95-100A-207
EMMS-AS-100-...	1220656	EAMM-U-110-S95-100A-207
EMMS-AS-140-...	1220582	EAMM-U-145-S95-140A-288
With gear unit		
EMGA-80-P-...	1589544	EAMM-U-110-S95-80G-207

- 1) The input torque must not exceed the maximum permissible transferable torque of the parallel kit.
- 2) Gear unit output shaft diameter: EMGA-60-P-...-SAS/-SST11 mm; EMGA-60-P-...-EAS, EMGC-60-P14 mm.



Note


Clamping element EADT for adjusting the toothed belt pretension with EAMM-U-110 and EAMM-U-145 → Page 21

Parallel kits EAMM-U...-D/S

Product range overview

FESTO

Permissible axis/motor combinations with spindle axis EGC-BS



- The kit can be mounted in all directions
- A counter bearing EAMG and a clamping sleeve EAMH-...-P with integrated trunnion are included in the scope of delivery of the parallel kit to provide support for the axis shaft
- Third-party motors can be connected. You can find out which motors are permitted from your local Festo contact or from
→ www.festo.com/sp/eamm

Motor / gear unit ¹⁾	Parallel kit	
Type	Part No.	Type
EGC-70-BS		
With servo motor		
EMME-AS-40-...	★ 2155239	EAMM-U-50-S38-40P-78
EMMS-AS-40-...	1217708	EAMM-U-50-S38-40A-78
EMMS-AS-55-...	1218538	EAMM-U-60-S38-55A-91
With stepper motor		
EMMS-ST-42-...	★ 1217945	EAMM-U-50-S38-42A-78
EMMS-ST-57-...	★ 1218568	EAMM-U-60-S38-57A-91
With gear unit		
EMGA-40-P-...	2283732	EAMM-U-60-S38-40G-91
EMGC-40-P-...	2283732	EAMM-U-60-S38-40G-91
EGC-80-BS		
With servo motor		
EMMS-AS-55-...	1219370	EAMM-U-60-S48-55A-91
EMMT-AS-60-...	★ 2629253	EAMM-U-70-S48-60P-96
EMME-AS-60-...	★ 2629253	EAMM-U-70-S48-60P-96
EMMS-AS-70-...	2787320	EAMM-U-70-S48-70A-96
EMMS-AS-70-...	1217689	EAMM-U-86-S48-70A-102
With stepper motor		
EMMS-ST-57-...	1219379	EAMM-U-60-S48-57A-91
EMMS-ST-87-...	1217604	EAMM-U-86-S48-87A-177
With gear unit		
EMGA-40-P-...	2283760	EAMM-U-60-S48-40G-91
EMGC-40-P-...	2283760	EAMM-U-60-S48-40G-91
EMGA-60-P-...-SAS/ SST ²⁾	2283760	EAMM-U-70-S48-60G-96
EMGA-60-P-...-EAS, EMGC-60-P-... ²⁾	2801715	EAMM-U-70-S48-60H-96
EMGA-60-P-...-SAS/ SST ²⁾	1587251	EAMM-U-86-S48-60G-102
EMGA-60-P-...-EAS, EMGC-60-P-... ²⁾	1587338	EAMM-U-86-S48-60H-102

Motor / gear unit ¹⁾	Parallel kit	
Type	Part No.	Type
EGC-120-BS		
With servo motor		
EMMS-AS-70-...	1217543	EAMM-U-86-S62-70A-177
EMME-AS-80-...	★ 2157004	EAMM-U-86-S62-80P-177
EMME-AS-100-...	★ 1217381	EAMM-U-110-S62-100A-207
EMMS-AS-100-...	★ 1217381	EAMM-U-110-S62-100A-207
EMMS-AS-140-...	★ 1219440	EAMM-U-145-S62-140A-288
With stepper motor		
EMMS-ST-87-...	★ 1217373	EAMM-U-86-S62-87A-177
With gear unit		
EMGA-60-P-...-SAS/ SST ²⁾	1587411	EAMM-U-86-S62-60G-177
EMGA-60-P-...-EAS, EMGC-60-P-... ²⁾	1587453	EAMM-U-86-S62-60H-177
EGC-185-BS		
With servo motor		
EMME-AS-100-...	1220656	EAMM-U-110-S95-100A-207
EMMS-AS-100-...	1220656	EAMM-U-110-S95-100A-207
EMMS-AS-140-...	1220582	EAMM-U-145-S95-140A-288
With gear unit		
EMGA-80-P-...	1589544	EAMM-U-110-S95-80G-207

1) The input torque must not exceed the maximum permissible transferable torque of the parallel kit.

2) Gear unit output shaft diameter: EMGA-60-P-...-SAS/-SST11 mm; EMGA-60-P-...-EAS, EMGC-60-P14 mm.



Note

Clamping element EADT for adjusting the toothed belt pretension with EAMM-U-110 and EAMM-U-145 → Page 21

Festo core product range

★ Generally ready for shipping ex works in 24 hours


★ Generally ready for shipping ex works in 5 days

Parallel kits EAMM-U-...-D/S

Product range overview

FESTO

Permissible axis/motor combinations with spindle axis with heavy-duty guide EGC-HD-BS




- A counter bearing EAMG and a clamping sleeve EAMH-...-P with integrated trunnion are included in the scope of delivery of the parallel kit to provide support for the axis shaft
- Third-party motors can be connected. You can find out which motors are permitted from your local Festo contact or from
→ www.festo.com/sp/eamm

Motor / gear unit ¹⁾	Parallel kit	
Type	Part No.	Type
EGC-HD-125		
With servo motor		
EMME-AS-40-...	★ 2155239	EAMM-U-50-S38-40P-78
EMMS-AS-40-...	1217708	EAMM-U-50-S38-40A-78
EMMS-AS-55-...	1218538	EAMM-U-60-S38-55A-91
With stepper motor		
EMMS-ST-42-...	★ 1217945	EAMM-U-50-S38-42A-78
EMMS-ST-57-...	1218568	EAMM-U-60-S38-57A-91
With gear unit		
EMGA-40-P-...	2283732	EAMM-U-60-S38-40G-91
EMGC-40-P-...	2283732	EAMM-U-60-S38-40G-91
EGC-HD-160		
With servo motor		
EMMS-AS-55-...	1219370	EAMM-U-60-S48-55A-91
EMMT-AS-60-...	★ 2629253	EAMM-U-70-S48-60P-96
EMME-AS-60-...	★ 2629253	EAMM-U-70-S48-60P-96
EMMS-AS-70-...	2787320	EAMM-U-70-S48-70A-96
EMMS-AS-70-...	1217689	EAMM-U-86-S48-70A-102
With stepper motor		
EMMS-ST-57-...	★ 1219379	EAMM-U-60-S48-57A-91
EMMS-ST-87-...	★ 1217604	EAMM-U-86-S48-87A-177
With gear unit		
EMGA-40-P-...	2283760	EAMM-U-60-S48-40G-91
EMGC-40-P-...	2283760	EAMM-U-60-S48-40G-91
EMGA-60-P-...-SAS/ SST ²⁾	2801627	EAMM-U-70-S48-60G-96
EMGA-60-P-...-EAS, EMGC-60-P-... ²⁾	2801715	EAMM-U-70-S48-60H-96
EMGA-60-P-...-SAS/ SST ²⁾	1587251	EAMM-U-86-S48-60G-102
EMGA-60-P-...-EAS, EMGC-60-P-... ²⁾	1587338	EAMM-U-86-S48-60H-102

Motor / gear unit ¹⁾	Parallel kit	
Type	Part No.	Type
EGC-HD-220		
With servo motor		
EMMS-AS-70-...	1217543	EAMM-U-86-S62-70A-177
EMME-AS-80-...	★ 2157004	EAMM-U-86-S62-80P-177
EMME-AS-100-...	1217381	EAMM-U-110-S62-100A-207
EMMS-AS-100-...	1217381	EAMM-U-110-S62-100A-207
EMMS-AS-140-...	1219440	EAMM-U-145-S62-140A-288
With stepper motor		
EMMS-ST-87-...	★ 1217373	EAMM-U-86-S62-87A-177
With gear unit		
EMGA-60-P-...-SAS/ SST ²⁾	1587411	EAMM-U-86-S62-60G-177
EMGA-60-P-...-EAS, EMGC-60-P-... ²⁾	1587453	EAMM-U-86-S62-60H-177

- 1) The input torque must not exceed the maximum permissible transferable torque of the parallel kit.
- 2) Gear unit output shaft diameter: EMGA-60-P-...-SAS/-SST11 mm; EMGA-60-P-...-EAS, EMGC-60-P14 mm.



Note

Clamping element EADT for adjusting the toothed belt pretension with EAMM-U-110 and EAMM-U-145 → Page 21


Parallel kits EAMM-U-...-D/S

Technical data

FESTO

Materials:

Housing: Wrought aluminium alloy
Clamping sleeve, toothed belt pulley:
Corrosion-resistant steel
Toothed belt: Polychloroprene
Screws: Galvanised steel



General technical data							
Type	For axis	Transferable torque [Nm]	Mass moment of inertia [kgmm ²]	Max. rotational speed [rpm]	No-load driving torque [Nm]	Weight [g]	→ Page
EAMM-U-50-D32-32B-78	ESBF, EGSL	1	12.1	6000	0.01	608	17
EAMM-U-50-D32-40A-78	ESBF, EGSL					600	
EAMM-U-50-D32-40A-78-S1	ESBF					620	
EAMM-U-50-D32-40P-78	ESBF, EGSL					596	
EAMM-U-50-D32-40P-78-S1	ESBF					610	
EAMM-U-50-D32-42A-78	ESBF, EGSL					610	
EAMM-U-50-D32-42A-78-S1	ESBF					630	
EAMM-U-50-S38-40A-78	ELGA-BS, EGC-BS, EGC-HD-BS	3	26.7	6000	0.07	580	20
EAMM-U-50-S38-40P-78						577	
EAMM-U-50-S38-42A-78						590	
EAMM-U-60-D32-40G-91	ESBF, EGSL					1100	17
EAMM-U-60-D32-40G-91-S1	ESBF					1140	
EAMM-U-60-D32-42B/C-91	ESBF, EGSL					1100	
EAMM-U-60-D32-42B/C-91-S1	ESBF					1140	
EAMM-U-60-D32-55A-91	ESBF, EGSL					1050	
EAMM-U-60-D32-55A-91-S1	ESBF					1100	
EAMM-U-60-D32-57A-91	ESBF, EGSL					1160	
EAMM-U-60-D32-57A-91-S1	ESBF					1190	
EAMM-U-60-D40-40G-91	ESBF, EGSL					1080	
EAMM-U-60-D40-40G-91-S1	ESBF					1130	
EAMM-U-60-D40-42B/C-91	ESBF, EGSL					1080	
EAMM-U-60-D40-42B/C-91-S1	ESBF					1130	
EAMM-U-60-D40-55A-91	ESBF, EGSL					1040	
EAMM-U-60-D40-55A-91-S1	ESBF					1080	
EAMM-U-60-D40-57A-91	ESBF, EGSL					1140	
EAMM-U-60-D40-57A-91-S1	ESBF					1170	
EAMM-U-60-S38-40G-91	ELGA-BS, EGC-BS, EGC-HD-BS	7	118	5000	0.18	1040	20
EAMM-U-60-S38-55A-91						990	
EAMM-U-60-S38-57A-91						1090	
EAMM-U-60-S48-40G-91						1110	
EAMM-U-60-S48-55A-91						1060	
EAMM-U-60-S48-57A-91						1160	
EAMM-U-70-D32-52B/C-96	ESBF, EGSL					1800	17
EAMM-U-70-D32-52B/C-96-S1	ESBF					1820	
EAMM-U-70-D32-60G-96	ESBF, EGSL					1760	
EAMM-U-70-D32-60G-96-S1	ESBF					1790	
EAMM-U-70-D32-60H-96	ESBF, EGSL					1750	
EAMM-U-70-D32-60H-96-S1	ESBF					1780	
EAMM-U-70-D32-60P-96	ESBF, EGSL					1750	
EAMM-U-70-D32-60P-96-S1	ESBF					1770	
EAMM-U-70-D32-70A-96	ESBF, EGSL					1720	
EAMM-U-70-D32-70A-96-S1	ESBF					1750	

Parallel kits EAMM-U-...-D/S

Technical data

General technical data							
Type	For axis	Transferable torque [Nm]	Mass moment of inertia [kgmm ²]	Max. rotational speed [rpm]	No-load driving torque [Nm]	Weight [g]	→ Page
EAMM-U-70-D40-52B/C-96	ESBF, EGSL	7	118	5000	0.18	1780	17, 14
EAMM-U-70-D40-52B/C-96-S1	ESBF					1800	
EAMM-U-70-D40-60G-96	ESBF, EGSL					1740	
EAMM-U-70-D40-60G-96-S1	ESBF					1770	
EAMM-U-70-D40-60H-96	ESBF, EGSL					1730	
EAMM-U-70-D40-60H-96-S1	ESBF					1760	
EAMM-U-70-D40-60P-96	ESBF, EGSL					1730	
EAMM-U-70-D40-60P-96-S1	ESBF					1750	
EAMM-U-70-D40-70A-96	ESBF, EGSL					1700	
EAMM-U-70-D40-70A-96-S1	ESBF					1730	
EAMM-U-70-D50-70A-96	ESBF					1700	
EAMM-U-70-D50-70A-96-S1	ESBF					1730	
EAMM-U-70-S48-60G-96	ELGA-BS, EGC-BS, EGC-HD-BS	7	118	5000	0.18	1780	17
EAMM-U-70-S48-60H-96						1780	
EAMM-U-70-S48-60P-96						1790	
EAMM-U-70-S48-70A-96						1750	
EAMM-U-86-D40-52B/C-102	ESBF, EGSL	9.5	175	5000	0.25	2520	18
EAMM-U-86-D40-52B/C-102-S1	ESBF					2540	
EAMM-U-86-D40-60G-102	ESBF, EGSL					2480	
EAMM-U-86-D40-60G-102-S1	ESBF					2500	
EAMM-U-86-D40-60H-102	ESBF, EGSL					2470	
EAMM-U-86-D40-60H-102-S1	ESBF					2490	
EAMM-U-86-D40-70A-102	ESBF, EGSL					2450	
EAMM-U-86-D40-70A-102-S1	ESBF					2460	
EAMM-U-86-D40-80P-102	ESBF, EGSL					2300	
EAMM-U-86-D40-80P-102-S1	ESBF					2320	
EAMM-U-86-D40-87A-102	ESBF, EGSL					2510	
EAMM-U-86-D40-87A-102-S1	ESBF					2530	
EAMM-U-86-D50-80P-102	ESBF	9.5	175	5000	0.25	2330	14
EAMM-U-86-D50-80P-102-S1						2350	
EAMM-U-86-D50-87A-102						2550	
EAMM-U-86-D50-87A-102-S1						2560	
EAMM-U-86-D50-60H-102						2500	
EAMM-U-86-D50-60H-102-S1						2520	
EAMM-U-86-D50-60G-102						2510	
EAMM-U-86-D50-60G-102-S1						2530	
EAMM-U-86-D60-52B/C-102	ESBF, EGSL	9.5	175	5000	0.25	2520	18
EAMM-U-86-D60-52B/C-102-S1	ESBF					2540	
EAMM-U-86-D60-60G-102	ESBF, EGSL					2480	
EAMM-U-86-D60-60G-102-S1	ESBF					2500	
EAMM-U-86-D60-60H-102	ESBF, EGSL					2470	
EAMM-U-86-D60-60H-102-S1	ESBF					2490	
EAMM-U-86-D60-70A-102	ESBF, EGSL					2440	
EAMM-U-86-D60-70A-102-S1	ESBF					2460	
EAMM-U-86-D60-80P-102	ESBF, EGSL					2300	
EAMM-U-86-D60-80P-102-S1	ESBF					2320	
EAMM-U-86-D60-87A-102	ESBF, EGSL					2510	
EAMM-U-86-D60-87A-102-S1	ESBF					2520	
EAMM-U-86-S48-60G-102	ELGA-BS, EGC-BS, EGC-HD-BS	9.5	175	5000	0.25	2480	20
EAMM-U-86-S48-60H-102						2470	
EAMM-U-86-S48-70A-102						2440	
EAMM-U-86-S48-87A-177						3270	
EAMM-U-86-S62-60G-177						3300	

Parallel kits EAMM-U-...-D/S

Technical data

FESTO

General technical data											
Type	For axis	Transferable torque [Nm]	Mass moment of inertia [kgmm ²]	Max. rotational speed [rpm]	No-load driving torque [Nm]	Weight [g]	➔ Page				
EAMM-U-86-S62-60H-177	ELGA-BS, EGC-BS, EGC-HD-BS	9.5	175	5000	0.25	3290	20				
EAMM-U-86-S62-70A-177						3270					
EAMM-U-86-S62-80P-177						3130					
EAMM-U-86-S62-87A-177						3330					
EAMM-U-110-D50-100A-120	ESBF	25	799	5000	0.3	4990	14				
EAMM-U-110-D50-100A-120-S1						5050					
EAMM-U-110-D50-60H-120						5280					
EAMM-U-110-D50-60H-120-S1						5310					
EAMM-U-110-D50-60G-120						5290					
EAMM-U-110-D50-60G-120-S1						5320					
EAMM-U-110-D50-80G-120						5160					
EAMM-U-110-D50-80G-120-S1						5220					
EAMM-U-110-D60-60G-120	ESBF, EGSL	25	799	5000	0.3	5250	17, 14				
EAMM-U-110-D60-60G-120-S1	ESBF					5080					
EAMM-U-110-D60-60H-120	ESBF, EGSL					5240					
EAMM-U-110-D60-60H-120-S1	ESBF					5270					
EAMM-U-110-D60-62B-120	ESBF, EGSL					5230					
EAMM-U-110-D60-62B-120-S1	ESBF					5270					
EAMM-U-110-D60-80G-120	ESBF, EGSL					5120					
EAMM-U-110-D60-80G-120-S1	ESBF					5180					
EAMM-U-110-D60-100A-120	ESBF, EGSL					4950					
EAMM-U-110-D60-100A-120-S1	ESBF					5020					
EAMM-U-110-D80-80G-120	ESBF									5240	14
EAMM-U-110-D80-80G-120-S1										5310	
EAMM-U-110-D80-100A-120										5070	
EAMM-U-110-D80-100A-120-S1										5140	
EAMM-U-110-S62-100A-207	ELGA-BS, EGC-BS, EGC-HD-BS	25	799	5000	0.3	6900	20				
EAMM-U-110-S95-100A-207	EGC-BS					6810					
EAMM-U-110-S95-80G-207	EGC-BS					6940					
EAMM-U-145-D80-140A-188	ESBF	50	2270	4000	2.0	11900	14				
EAMM-U-145-D80-140A-188-S1						12100					
EAMM-U-145-D100-120G-188						12000					
EAMM-U-145-D100-120G-188-S1						12100					
EAMM-U-145-D100-140A-188						11800					
EAMM-U-145-D100-140A-188-S1						11900					
EAMM-U-145-S62-140A-288	ELGA-BS, EGC-BS, EGC-HD-BS					15030	20				
EAMM-U-145-S95-140A-288	ELGA-BS, EGC-BS					14850					

Operating and environmental conditions		
Gear ratio		1:1
Ambient temperature	[°C]	-10 ... +60
Storage temperature	[°C]	-25 ... +60
Protection class ¹⁾		
EAMM-U-...		IP40
EAMM-U-...-S1		IP65
Relative air humidity	[%]	0 ... 95
Corrosion resistance class CRC ²⁾		2
Note on materials		RoHS-compliant

1) Only in combination with attached motor and axis.

2) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

Parallel kits EAMM-U-...-D/S


Technical data

FESTO

Dimensions and ordering data

Download CAD data → www.festo.com

ESBF-BS-...



Type	B1	B2	D1	H1	H2 ±1	H3	H4	L1	T1	Part No.	Type							
EAMM-U-50-D32-40A-78	50	32.5	M6	128.8	78	22.8	32.5	45	15	1201591	EAMM-U-50-D32-40A-78							
EAMM-U-50-D32-40A-78-S1										1202302	EAMM-U-50-D32-40A-78-S1							
EAMM-U-50-D32-40P-78										★2153283	EAMM-U-50-D32-40P-78							
EAMM-U-50-D32-40P-78-S1										2154009	EAMM-U-50-D32-40P-78-S1							
EAMM-U-50-D32-42A-78										★1201607	EAMM-U-50-D32-42A-78							
EAMM-U-50-D32-42A-78-S1										1202312	EAMM-U-50-D32-42A-78-S1							
EAMM-U-60-D32-40G-91	60	32.5	M6	157	91.5	27.5	32.5	56	15	1577358	EAMM-U-60-D32-40G-91							
EAMM-U-60-D32-40G-91-S1										1577346	EAMM-U-60-D32-40G-91-S1							
EAMM-U-60-D32-55A-91										1210126	EAMM-U-60-D32-55A-91							
EAMM-U-60-D32-55A-91-S1										1210450	EAMM-U-60-D32-55A-91-S1							
EAMM-U-60-D32-57A-91										★1210419	EAMM-U-60-D32-57A-91							
EAMM-U-60-D32-57A-91-S1										1210453	EAMM-U-60-D32-57A-91-S1							
EAMM-U-60-D40-40G-91		38				38	1577165			EAMM-U-60-D40-40G-91								
EAMM-U-60-D40-40G-91-S1							1435968			EAMM-U-60-D40-40G-91-S1								
EAMM-U-60-D40-55A-91							1210438			EAMM-U-60-D40-55A-91								
EAMM-U-60-D40-55A-91-S1							1210458			EAMM-U-60-D40-55A-91-S1								
EAMM-U-60-D40-57A-91							★1210442			EAMM-U-60-D40-57A-91								
EAMM-U-60-D40-57A-91-S1							1210462			EAMM-U-60-D40-57A-91-S1								
EAMM-U-70-D32-60G-96							70			32.5	M6	173.5	96	34.5	64.5	15	2748181	EAMM-U-70-D32-60G-96
EAMM-U-70-D32-60G-96-S1																	2778302	EAMM-U-70-D32-60G-96-S1
EAMM-U-70-D32-60H-96	2778393	EAMM-U-70-D32-60H-96																
EAMM-U-70-D32-60H-96-S1	2781450	EAMM-U-70-D32-60H-96-S1																
EAMM-U-70-D32-60P-96	★2619586	EAMM-U-70-D32-60P-96																
EAMM-U-70-D32-60P-96-S1	2619688	EAMM-U-70-D32-60P-96-S1																
EAMM-U-70-D32-70A-96	2755565	EAMM-U-70-D32-70A-96																
EAMM-U-70-D32-70A-96-S1	2781711	EAMM-U-70-D32-70A-96-S1																
EAMM-U-70-D40-60G-96	38	38	2785471	EAMM-U-70-D40-60G-96														
EAMM-U-70-D40-60G-96-S1			2785542	EAMM-U-70-D40-60G-96-S1														
EAMM-U-70-D40-60H-96			2786101	EAMM-U-70-D40-60H-96														
EAMM-U-70-D40-60H-96-S1			2786137	EAMM-U-70-D40-60H-96-S1														
EAMM-U-70-D40-60P-96			★2617488	EAMM-U-70-D40-60P-96														
EAMM-U-70-D40-60P-96-S1			2546123	EAMM-U-70-D40-60P-96-S1														
EAMM-U-70-D40-70A-96			2786204	EAMM-U-70-D40-70A-96														
EAMM-U-70-D40-70A-96-S1			2786316	EAMM-U-70-D40-70A-96-S1														
EAMM-U-70-D50-70A-96			46.5	46.5	2786899	EAMM-U-70-D50-70A-96												
EAMM-U-70-D50-70A-96-S1					2756078	EAMM-U-70-D50-70A-96-S1												

Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ★ Generally ready for shipping ex works in 5 days

Parallel kits EAMM-U-...-D/S


Technical data

FESTO

Dimensions and ordering data

Download CAD data → www.festo.com

ESBF-BS-...



Type	B1	B2	D1	H1	H2 ±1	H3	H4	L1	T1	Part No.	Type
EAMM-U-86-D40-60G-102	86	38	M6	188.5	102.5	38	38	69	16	1586445	EAMM-U-86-D40-60G-102
EAMM-U-86-D40-60G-102-S1										1586429	EAMM-U-86-D40-60G-102-S1
EAMM-U-86-D40-60H-102										1586496	EAMM-U-86-D40-60H-102
EAMM-U-86-D40-60H-102-S1										1586372	EAMM-U-86-D40-60H-102-S1
EAMM-U-86-D40-70A-102										1212826	EAMM-U-86-D40-70A-102
EAMM-U-86-D40-70A-102-S1										1212854	EAMM-U-86-D40-70A-102-S1
EAMM-U-86-D40-80P-102										★ 2802441	EAMM-U-86-D40-80P-102
EAMM-U-86-D40-80P-102-S1										2802656	EAMM-U-86-D40-80P-102-S1
EAMM-U-86-D40-87A-102										★ 1215802	EAMM-U-86-D40-87A-102
EAMM-U-86-D40-87A-102-S1										1215814	EAMM-U-86-D40-87A-102-S1
EAMM-U-86-D50-60G-102	86	46.5	M8	188.5	102.5	38	46.5	71	16	2803125	EAMM-U-86-D50-60G-102
EAMM-U-86-D50-60G-102-S1										2803197	EAMM-U-86-D50-60G-102-S1
EAMM-U-86-D50-60H-102										2803326	EAMM-U-86-D50-60H-102
EAMM-U-86-D50-60H-102-S1										2803325	EAMM-U-86-D50-60H-102-S1
EAMM-U-86-D50-80P-102										★ 2803053	EAMM-U-86-D50-80P-102
EAMM-U-86-D50-80P-102-S1										2803073	EAMM-U-86-D50-80P-102-S1
EAMM-U-86-D50-87A-102										★ 2802708	EAMM-U-86-D50-87A-102
EAMM-U-86-D50-87A-102-S1										2802742	EAMM-U-86-D50-87A-102-S1
EAMM-U-110-D50-60G-120	110	46.5	M8	225	120	45	46.5	82	16	2797368	EAMM-U-110-D50-60G-120
EAMM-U-110-D50-60G-120-S1										2798665	EAMM-U-110-D50-60G-120-S1
EAMM-U-110-D50-60H-120										2798760	EAMM-U-110-D50-60H-120
EAMM-U-110-D50-60H-120-S1										2799150	EAMM-U-110-D50-60H-120-S1
EAMM-U-110-D50-80G-120										2799196	EAMM-U-110-D50-80G-120
EAMM-U-110-D50-80G-120-S1										2799281	EAMM-U-110-D50-80G-120-S1
EAMM-U-110-D50-100A-120										★ 2799424	EAMM-U-110-D50-100A-120
EAMM-U-110-D50-100A-120-S1										2799488	EAMM-U-110-D50-100A-120-S1
EAMM-U-86-D60-52B/C-102	86	56.5	M8	188.5	102.5	38	56.5	71	16	1537000	EAMM-U-86-D60-52B/C-102
EAMM-U-86-D60-52B/C-102-S1										1431381	EAMM-U-86-D60-52B/C-102-S1
EAMM-U-86-D60-60G-102										1586347	EAMM-U-86-D60-60G-102
EAMM-U-86-D60-60G-102-S1										1437163	EAMM-U-86-D60-60G-102-S1
EAMM-U-86-D60-70A-102										1212477	EAMM-U-86-D60-70A-102
EAMM-U-86-D60-70A-102-S1										1212835	EAMM-U-86-D60-70A-102-S1
EAMM-U-86-D60-80P-102										★ 2155875	EAMM-U-86-D60-80P-102
EAMM-U-86-D60-80P-102-S1										2156527	EAMM-U-86-D60-80P-102-S1
EAMM-U-86-D60-87A-102										★ 1215784	EAMM-U-86-D60-87A-102
EAMM-U-86-D60-87A-102-S1										1215810	EAMM-U-86-D60-87A-102-S1

Festo core product range

★ Generally ready for shipping ex works in 24 hours

☆ Generally ready for shipping ex works in 5 days

Parallel kits EAMM-U-...-D/S


Technical data

FESTO

Dimensions and ordering data

Download CAD data → www.festo.com

ESBF-BS...



Type	B1	B2	D1	H1	H2 ±1	H3	H4	L1	T1	Part No.	Type
EAMM-U-110-D60-60G-120	110	56.5	M8	225	120	45	56.5	82	16	1543240	EAMM-U-110-D60-60G-120
EAMM-U-110-D60-60G-120-S1										1436183	EAMM-U-110-D60-60G-120-S1
EAMM-U-110-D60-60H-120										1542264	EAMM-U-110-D60-60H-120
EAMM-U-110-D60-60H-120-S1										1530621	EAMM-U-110-D60-60H-120-S1
EAMM-U-110-D60-62B-120										1536988	EAMM-U-110-D60-62B-120
EAMM-U-110-D60-62B-120-S1										1431443	EAMM-U-110-D60-62B-120-S1
EAMM-U-110-D60-80G-120										1532949	EAMM-U-110-D60-80G-120
EAMM-U-110-D60-80G-120-S1										1530875	EAMM-U-110-D60-80G-120-S1
EAMM-U-110-D60-100A-120										★ 1202436	EAMM-U-110-D60-100A-120
EAMM-U-110-D60-100A-120-S1										1203112	EAMM-U-110-D60-100A-120-S1
EAMM-U-110-D80-80G-120	110	72	M10	235	120	55	72	82	20.5	1589614	EAMM-U-110-D80-80G-120
EAMM-U-110-D80-80G-120-S1										1589706	EAMM-U-110-D80-80G-120-S1
EAMM-U-110-D80-100A-120										1465438	EAMM-U-110-D80-100A-120
EAMM-U-110-D80-100A-120-S1										1433650	EAMM-U-110-D80-100A-120-S1
EAMM-U-145-D80-140A-188	145	72	M10	348	188	70	72	99.5	25	1465530	EAMM-U-145-D80-140A-188
EAMM-U-145-D80-140A-188-S1										1433709	EAMM-U-145-D80-140A-188-S1
EAMM-U-145-D100-120G-188	145	89	M10	348	188	70	89	99.5	25	2803620	EAMM-U-145-D100-120G-188
EAMM-U-145-D100-120G-188-S1										2803622	EAMM-U-145-D100-120G-188-S1
EAMM-U-145-D100-140A-188										1465541	EAMM-U-145-D100-140A-188
EAMM-U-145-D100-140A-188-S1										1433852	EAMM-U-145-D100-140A-188-S1

Festo core product range

★ Generally ready for shipping ex works in 24 hours

☆ Generally ready for shipping ex works in 5 days

Parallel kits EAMM-U-...-D/S


Technical data

FESTO

Dimensions and ordering data

Download CAD data → www.festo.com

EGSL-...



Type	B1	B2	D1	H1	H2 ±1	H3	H4	L1	T1 +0.2	Part No.	Type
EAMM-U-50-D32-32B-78	50	32.5	M6	128.8	78	22.8	32.5	45	15	1570862	EAMM-U-50-D32-32B-78
EAMM-U-50-D32-40A-78										1201591	EAMM-U-50-D32-40A-78
EAMM-U-50-D32-40A-78-S1										1202302	EAMM-U-50-D32-40A-78-S1
EAMM-U-50-D32-40P-78										★ 2153283	EAMM-U-50-D32-40P-78
EAMM-U-50-D32-40P-78-S1										2154009	EAMM-U-50-D32-40P-78-S1
EAMM-U-50-D32-42A-78										★ 1201607	EAMM-U-50-D32-42A-78
EAMM-U-50-D32-42A-78-S1										1202312	EAMM-U-50-D32-42A-78-S1
EAMM-U-60-D32-40G-91	60	32.5	M6	157	91.5	27.5	32.5	56	15	1577358	EAMM-U-60-D32-40G-91
EAMM-U-60-D32-40G-91-S1										1577346	EAMM-U-60-D32-40G-91-S1
EAMM-U-60-D32-42B/C-91										1577393	EAMM-U-60-D32-42B/C-91
EAMM-U-60-D32-42B/C-91-S1										1577380	EAMM-U-60-D32-42B/C-91-S1
EAMM-U-60-D32-55A-91										1210126	EAMM-U-60-D32-55A-91
EAMM-U-60-D32-55A-91-S1										1210450	EAMM-U-60-D32-55A-91-S1
EAMM-U-60-D32-57A-91										★ 1210419	EAMM-U-60-D32-57A-91
EAMM-U-60-D32-57A-91-S1										1210453	EAMM-U-60-D32-57A-91-S1
EAMM-U-60-D40-40G-91		38	M6	157	91.5	27.5	38	56	15	1577165	EAMM-U-60-D40-40G-91
EAMM-U-60-D40-40G-91-S1										1435968	EAMM-U-60-D40-40G-91-S1
EAMM-U-60-D40-42B/C-91										1570950	EAMM-U-60-D40-42B/C-91
EAMM-U-60-D40-42B/C-91-S1										1430735	EAMM-U-60-D40-42B/C-91-S1
EAMM-U-60-D40-55A-91										1210438	EAMM-U-60-D40-55A-91
EAMM-U-60-D40-55A-91-S1										1210458	EAMM-U-60-D40-55A-91-S1
EAMM-U-60-D40-57A-91										★ 1210442	EAMM-U-60-D40-57A-91
EAMM-U-60-D40-57A-91-S1										1210462	EAMM-U-60-D40-57A-91-S1
EAMM-U-70-D32-52B/C-96	70	32.5	M6	173.5	96	34.5	32.5	64.5	15	2755890	EAMM-U-70-D32-52B/C-96
EAMM-U-70-D32-52B/C-96-S1										2781778	EAMM-U-70-D32-52B/C-96-S1
EAMM-U-70-D32-60G-96										2748181	EAMM-U-70-D32-60G-96
EAMM-U-70-D32-60G-96-S1										2778302	EAMM-U-70-D32-60G-96-S1
EAMM-U-70-D32-60H-96										2778393	EAMM-U-70-D32-60H-96
EAMM-U-70-D32-60H-96-S1										2781450	EAMM-U-70-D32-60H-96-S1
EAMM-U-70-D32-60P-96										★ 2619586	EAMM-U-70-D32-60P-96
EAMM-U-70-D32-60P-96-S1										2619688	EAMM-U-70-D32-60P-96-S1

Festo core product range

★ Generally ready for shipping ex works in 24 hours

☆ Generally ready for shipping ex works in 5 days

Parallel kits EAMM-U-...-D/S


Technical data

FESTO

Dimensions and ordering data

Download CAD data → www.festo.com

EGSL-...



Type	B1	B2	D1	H1	H2 ±1	H3	H4	L1	T1 +0.2	Part No.	Type
EAMM-U-70-D32-70A-96	70	32.5	M6	173.5	96	34.5	32.5	64.5	15	2755565	EAMM-U-70-D32-70A-96
EAMM-U-70-D32-70A-96-S1										2781711	EAMM-U-70-D32-70A-96-S1
EAMM-U-70-D40-52B/C-96	70	38	M6	173.5	96	34.5	38	64.5	15	2786802	EAMM-U-70-D40-52B/C-96
EAMM-U-70-D40-52B/C-96-S1										2786845	EAMM-U-70-D40-52B/C-96-S1
EAMM-U-70-D40-60G-96										2785471	EAMM-U-70-D40-60G-96
EAMM-U-70-D40-60G-96-S1										2785542	EAMM-U-70-D40-60G-96-S1
EAMM-U-70-D40-60H-96										2786101	EAMM-U-70-D40-60H-96
EAMM-U-70-D40-60H-96-S1										2786137	EAMM-U-70-D40-60H-96-S1
EAMM-U-70-D40-60P-96										★ 2617488	EAMM-U-70-D40-60P-96
EAMM-U-70-D40-60P-96-S1										2546123	EAMM-U-70-D40-60P-96-S1
EAMM-U-70-D40-70A-96										2786204	EAMM-U-70-D40-70A-96
EAMM-U-70-D40-70A-96-S1										2786316	EAMM-U-70-D40-70A-96-S1
EAMM-U-86-D40-52B/C-102	86	38	M6	188.5	102.5	38	38	69	16	1537046	EAMM-U-86-D40-52B/C-102
EAMM-U-86-D40-52B/C-102-S1										1537011	EAMM-U-86-D40-52B/C-102-S1
EAMM-U-86-D40-60G-102										1586445	EAMM-U-86-D40-60G-102
EAMM-U-86-D40-60G-102-S1										1586429	EAMM-U-86-D40-60G-102-S1
EAMM-U-86-D40-60H-102										1586496	EAMM-U-86-D40-60H-102
EAMM-U-86-D40-60H-102-S1										1586372	EAMM-U-86-D40-60H-102-S1
EAMM-U-86-D40-70A-102										1212826	EAMM-U-86-D40-70A-102
EAMM-U-86-D40-70A-102-S1										1212854	EAMM-U-86-D40-70A-102-S1
EAMM-U-86-D40-80P-102										★ 2802441	EAMM-U-86-D40-80P-102
EAMM-U-86-D40-80P-102-S1										2802656	EAMM-U-86-D40-80P-102-S1
EAMM-U-86-D40-87A-102										★ 1215802	EAMM-U-86-D40-87A-102
EAMM-U-86-D40-87A-102-S1										1215814	EAMM-U-86-D40-87A-102-S1

Festo core product range

★ Generally ready for shipping ex works in 24 hours

☆ Generally ready for shipping ex works in 5 days

Parallel kits EAMM-U...-D/S


Technical data

FESTO

Dimensions and ordering data

Download CAD data → www.festo.com

EGSL...



Type	B1	B2	D1	H1	H2 ±1	H3	H4	L1	T1 +0.2	Part No.	Type
EAMM-U-86-D60-52B/C-102	86	56.5	M8	188.5	102.5	38	56.5	71	16	1537000	EAMM-U-86-D60-52B/C-102
EAMM-U-86-D60-52B/C-102-S1										1431381	EAMM-U-86-D60-52B/C-102-S1
EAMM-U-86-D60-60G-102										1586347	EAMM-U-86-D60-60G-102
EAMM-U-86-D60-60G-102-S1										1437163	EAMM-U-86-D60-60G-102-S1
EAMM-U-86-D60-60H-102										1586276	EAMM-U-86-D60-60H-102
EAMM-U-86-D60-60H-102-S1										1530837	EAMM-U-86-D60-60H-102-S1
EAMM-U-86-D60-70A-102										1212477	EAMM-U-86-D60-70A-102
EAMM-U-86-D60-70A-102-S1										1212835	EAMM-U-86-D60-70A-102-S1
EAMM-U-86-D60-80P-102										★ 2155875	EAMM-U-86-D60-80P-102
EAMM-U-86-D60-80P-102-S1										2156527	EAMM-U-86-D60-80P-102-S1
EAMM-U-86-D60-87A-102										★ 1215784	EAMM-U-86-D60-87A-102
EAMM-U-86-D60-87A-102-S1										1215810	EAMM-U-86-D60-87A-102-S1
EAMM-U-110-D60-60G-120	110	56.5	M8	225	120	45	56.5	82	16	1543240	EAMM-U-110-D60-60G-120
EAMM-U-110-D60-60G-120-S1										1436183	EAMM-U-110-D60-60G-120-S1
EAMM-U-110-D60-60H-120										1542264	EAMM-U-110-D60-60H-120
EAMM-U-110-D60-60H-120-S1										1530621	EAMM-U-110-D60-60H-120-S1
EAMM-U-110-D60-62B-120										1536988	EAMM-U-110-D60-62B-120
EAMM-U-110-D60-62B-120-S1										1431443	EAMM-U-110-D60-62B-120-S1
EAMM-U-110-D60-80G-120										1532949	EAMM-U-110-D60-80G-120
EAMM-U-110-D60-80G-120-S1										1530875	EAMM-U-110-D60-80G-120-S1
EAMM-U-110-D60-100A-120										★ 1202436	EAMM-U-110-D60-100A-120
EAMM-U-110-D60-100A-120-S1										1203112	EAMM-U-110-D60-100A-120-S1

Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ★ Generally ready for shipping ex works in 5 days

Parallel kits EAMM-U-...-D/S

Technical data

FESTO

Dimensions and ordering data

Download CAD data → www.festo.com

ELGA-BS/EGC-BS/EGC-HD-BS




Illustration:

- 1 Parallel kit
- 2 Spindle axis
- 3 Motor

Type	B1	H1	H2 ±1	H3	L1	Part No.	Type
EAMM-U-50-S38-40A-78	50	131	78	25	43	1217708	EAMM-U-50-S38-40A-78
EAMM-U-50-S38-40P-78						★ 2155239	EAMM-U-50-S38-40P-78
EAMM-U-50-S38-42A-78						★ 1217945	EAMM-U-50-S38-42A-78
EAMM-U-60-S38-40G-91	60	157	91.5	27.5	53	2283732	EAMM-U-60-S38-40G-91
EAMM-U-60-S38-55A-91						1218538	EAMM-U-60-S38-55A-91
EAMM-U-60-S38-57A-91						★ 1218568	EAMM-U-60-S38-57A-91
EAMM-U-60-S48-40G-91	60	161.5	91.5	32	54	2283760	EAMM-U-60-S48-40G-91
EAMM-U-60-S48-55A-91						1219370	EAMM-U-60-S48-55A-91
EAMM-U-60-S48-57A-91						★ 1219379	EAMM-U-60-S48-57A-91
EAMM-U-70-S48-60G-96	70	173.5	96	34.5	64.5	2801627	EAMM-U-70-S48-60G-96
EAMM-U-70-S48-60H-96						2801715	EAMM-U-70-S48-60H-96
EAMM-U-70-S48-60P-96						★ 2629253	EAMM-U-70-S48-60P-96
EAMM-U-70-S48-70A-96	86	188.5	102.5	38	67	2787320	EAMM-U-70-S48-70A-96
EAMM-U-86-S48-60G-102						1587251	EAMM-U-86-S48-60G-102
EAMM-U-86-S48-60H-102						1587338	EAMM-U-86-S48-60H-102
EAMM-U-86-S48-70A-102	86	268.5	177.5	43	69	1217689	EAMM-U-86-S48-70A-102
EAMM-U-86-S48-87A-177						★ 1217604	EAMM-U-86-S48-87A-177
EAMM-U-86-S62-60G-177						1587411	EAMM-U-86-S62-60G-177
EAMM-U-86-S62-60H-177	86	268.5	177.5	43	69	1587453	EAMM-U-86-S62-60H-177
EAMM-U-86-S62-70A-177						1217543	EAMM-U-86-S62-70A-177
EAMM-U-86-S62-80P-177						★ 2157004	EAMM-U-86-S62-80P-177
EAMM-U-86-S62-87A-177	110	322.5	207.5	55	82	★ 1217373	EAMM-U-86-S62-87A-177
EAMM-U-110-S62-100A-207						★ 1217381	EAMM-U-110-S62-100A-207
EAMM-U-110-S95-80G-207						1589544	EAMM-U-110-S95-80G-207
EAMM-U-110-S95-100A-207	145	448	288	70	99.5	1220656	EAMM-U-110-S95-100A-207
EAMM-U-145-S62-140A-288						1219440	EAMM-U-145-S62-140A-288
EAMM-U-145-S95-140A-288						1220582	EAMM-U-145-S95-140A-288

Festo core product range

- ★ Generally ready for shipping ex works in 24 hours
- ★ Generally ready for shipping ex works in 5 days

Parallel kits EAMM-U-...-D/S

Accessories

Clamping element EADT

Materials:

Polymer

RoHS compliant

This enables high toothed belt pretension forces to be generated with low torques at the clamping element.

For setting the toothed belt pretension with EAMM-U-110 and EAMM-U-145. The motor is pushed away from the axis mechanism by turning the clamping element secured in a hole in the housing (the motor can be moved in a slot for this purpose).

Can only be used in combination with parallel kit EAMM-U-...-D/S.



Ordering data					
Type	Ambient temperature [°C]	Weight [g]	Part No.	Type	
EADT-E-U1-110	-10 ... +60	9	1461069	EADT-E-U1-110	

Counter bearing EAMG

Materials:

Wrought aluminium alloy

RoHS compliant

Can only be used in combination with parallel kit EAMM-U-...-D/S.

A counter bearing EAMG reduces the load on the axis or motor bearings to improve the service life under high loads. A clamping sleeve EAMH-...-P is additionally required for each counter bearing.



Ordering data						
Type	For size	Max. rotational speed [rpm]	Ambient temperature [°C]	Weight [g]	Part No.	Type
EAMG-U1-50	50	6000	-10 ... +60	20	1354281	EAMG-U1-50
EAMG-U1-60-G2	60	6000		35	4164963	EAMG-U1-60-G2
EAMG-U1-70	70	5000		74	2598638	EAMG-U1-70
EAMG-U1-86	86	5000		83	1354283	EAMG-U1-86
EAMG-U1-110	110	5000		169	1354284	EAMG-U1-110
EAMG-U1-145	145	4000		186	1354285	EAMG-U1-145

Parallel kits EAMM-U-...-D/S

Accessories

FESTO

Clamping sleeve EAMH-...-P, with trunnion

Materials:

Corrosion-resistant steel

RoHS compliant

Can only be used in combination
with parallel kit EAMM-U-...-D/S.

To retrofit the counter bearing, the clamping sleeve without trunnion included as standard in the parallel kit must be replaced by the clamping sleeve EAMH-...-P with integrated trunnion. The appropriate clamping sleeve size for the counter bearing is determined by the size of the parallel kit.



Ordering data								
Type	For size	For shaft Ø, motor/axis Ø h7 ... k7	Max. rotational speed [rpm]	Mass moment of inertia [kg mm ²]	Ambient temperature [°C]	Weight [g]	Part No.	Type
EAMH-50-5-C13.6-P	50	5	6000	0.39	-10 ... +60	20	1354092	EAMH-50-5-C13.6-P
EAMH-50-6-C13.6-P	50	6	6000	0.38		19	1354093	EAMH-50-6-C13.6-P
EAMH-50-8-C13.6-P	50	8	6000	0.35		16	1354094	EAMH-50-8-C13.6-P
EAMH-60-6-C18.1-P	60	6	6000	1.57		44	1354095	EAMH-60-6-C18.1-P
EAMH-60-6.35-C18.1-P	60	6.35	6000	1.56		43	1354096	EAMH-60-6.35-C18.1-P
EAMH-60-8-C18.1-P	60	8	6000	1.53		41	1354097	EAMH-60-8-C18.1-P
EAMH-60-9-C18.1-P	60	9	6000	1.5		39	1354098	EAMH-60-9-C18.1-P
EAMH-60-10-C18.1-P	60	10	6000	1.4		38	1545242	EAMH-60-10-C18.1-P
EAMH-60-11-C18.1-P	60	11	6000	1.31		35	2789343	EAMH-60-11-C18.1-P
EAMH-60-12-C18.1-P	60	12	6000	1.3		32	1354099	EAMH-60-12-C18.1-P
EAMH-86-6-C27.3-P	70, 86	6	5000	12.3		123	2789351	EAMH-86-6-C27.3-P
EAMH-86-8-C27.3-P	70, 86	8	5000	10.3		128	1354100	EAMH-86-8-C27.3-P
EAMH-86-9-C27.3-P	70, 86	9	5000	9		117	2789359	EAMH-86-9-C27.3-P
EAMH-86-10-C27.3-P	70, 86	10	5000	9		115	2789365	EAMH-86-10-C27.3-P
EAMH-86-11-C27.3-P	70, 86	11	5000	10.1		119	1354101	EAMH-86-11-C27.3-P
EAMH-86-12-C27.3-P	70, 86	12	5000	10		115	1354102	EAMH-86-12-C27.3-P
EAMH-86-14-C27.3-P	70, 86	14	5000	8.74		103	1459337	EAMH-86-14-C27.3-P
EAMH-86-16-C27.3-P	70, 86	16	5000	8.3		95	2430402	EAMH-86-16-C27.3-P
EAMH-86-19-C27.3-P	70, 86	19	5000	7.1		78	2406019	EAMH-86-19-C27.3-P
EAMH-110-11-C34-P	110	11	5000	33.2		270	1545245	EAMH-110-11-C34-P
EAMH-110-12-C34-P	110	12	5000	36.3		278	1354103	EAMH-110-12-C34-P
EAMH-110-14-C34-P	110	14	5000	35.8		267	1354104	EAMH-110-14-C34-P
EAMH-110-16-C34-P	110	16	5000	35.1		254	1354105	EAMH-110-16-C34-P
EAMH-110-19-C34-P	110	19	5000	33.3		230	1354106	EAMH-110-19-C34-P
EAMH-110-20-C34-P	110	20	5000	30.2		217	1545246	EAMH-110-20-C34-P
EAMH-110-22-C34-P	110	22	5000	28.3		200	2430414	EAMH-110-22-C34-P
EAMH-110-25-C34-P	110	25	5000	25.8		170	1354107	EAMH-110-25-C34-P
EAMH-145-12-C34-P	145	12	4000	43.9		338	1354108	EAMH-145-12-C34-P
EAMH-145-19-C34-P	145	19	4000	38		281	1459342	EAMH-145-19-C34-P
EAMH-145-24-C34-P	145	24	4000	34		229	1354109	EAMH-145-24-C34-P
EAMH-145-25-C34-P	145	25	4000	32.1		217	1354110	EAMH-145-25-C34-P

Parallel kits EAMM-U-...-D/S

Accessories

FESTO

Clamping sleeve EAMH, without trunnion

Materials:

Corrosion-resistant steel

RoHS compliant

Can only be used in combination with parallel kit EAMM-U-...-D/S.

Clamping sleeves for adapting third-party motors with deviating shaft diameters to the parallel kits.



Ordering data								
Type	For size	For shaft Ø, motor/axis	Max. rotational speed	Mass moment of inertia	Ambient temperature	Weight	Part No.	Type
		Ø h7 ... k7	[rpm]	[kg mm ²]	[°C]	[g]		
EAMH-50-5-C13.6	50	5	6000	0.44	-10 ... +60	19	2428478	EAMH-50-5-C13.6
EAMH-50-6-C13.6	50	6	6000	0.43		19	2428479	EAMH-50-6-C13.6
EAMH-50-8-C13.6	50	8	6000	0.40		16	2428480	EAMH-50-8-C13.6
EAMH-60-6-C18.1	60	6	6000	1.46		36	2428515	EAMH-60-6-C18.1
EAMH-60-6.35-C18.1	60	6.35	6000	1.46		36	2428516	EAMH-60-6.35-C18.1
EAMH-60-8-C18.1	60	8	6000	1.44		34	2428517	EAMH-60-8-C18.1
EAMH-60-9-C18.1	60	9	6000	1.42		32	2428518	EAMH-60-9-C18.1
EAMH-60-10-C18.1	60	10	6000	1.38		30	2428519	EAMH-60-10-C18.1
EAMH-60-11-C18.1	60	11	6000	1.31		28	2789160	EAMH-60-11-C18.1
EAMH-60-12-C18.1	60	12	6000	1.22		26	2428520	EAMH-60-12-C18.1
EAMH-86-6-C27.3	70, 86	6	5000	10.2		122	2789214	EAMH-86-6-C27.3
EAMH-86-8-C27.3	70, 86	8	5000	10.3		119	2429531	EAMH-86-8-C27.3
EAMH-86-9-C27.3	70, 86	9	5000	11.6		116	2789221	EAMH-86-9-C27.3
EAMH-86-10-C27.3	70, 86	10	5000	10.1		114	2789230	EAMH-86-10-C27.3
EAMH-86-11-C27.3	70, 86	11	5000	10.2		112	2429532	EAMH-86-11-C27.3
EAMH-86-12-C27.3	70, 86	12	5000	10.1		109	2429533	EAMH-86-12-C27.3
EAMH-86-14-C27.3	70, 86	14	5000	9.9		102	2429534	EAMH-86-14-C27.3
EAMH-86-16-C27.3	70, 86	16	5000	9.5		94	2430397	EAMH-86-16-C27.3
EAMH-86-19-C27.3	70, 86	19	5000	8.2		76	2429535	EAMH-86-19-C27.3
EAMH-110-11-C34	110	11	5000	32.2		233	2429555	EAMH-110-11-C34
EAMH-110-12-C34	110	12	5000	32.1		229	2429556	EAMH-110-12-C34
EAMH-110-14-C34	110	14	5000	31.8		219	2429557	EAMH-110-14-C34
EAMH-110-16-C34	110	16	5000	31.2		208	2429558	EAMH-110-16-C34
EAMH-110-19-C34	110	19	5000	29.9		188	2429559	EAMH-110-19-C34
EAMH-110-20-C34	110	20	5000	29.2		180	2429560	EAMH-110-20-C34
EAMH-110-22-C34	110	22	5000	27.3		162	2430411	EAMH-110-22-C34
EAMH-110-25-C34	110	25	5000	23.4		133	2429561	EAMH-110-25-C34
EAMH-145-12-C34	145	12	4000	38.1		274	2429590	EAMH-145-12-C34
EAMH-145-19-C34	145	19	4000	35.5		227	2429591	EAMH-145-19-C34
EAMH-145-24-C34	145	24	4000	30.0		177	2429592	EAMH-145-24-C34
EAMH-145-25-C34	145	25	4000	28.1		165	2429593	EAMH-145-25-C34

Parallel kits EAMM-U-...-D/S

Accessories

FESTO

Seal set

RoHS compliant


Spare part for degree of protection to IP65. Seal between:

- Motor and parallel kit
- Motor and gear unit
- Motor and geometry of customer equipment



- - Note

The seal reduces the dissipation of heat between the motor and flange. Note derating of motor.



Ordering data					
Type	For parallel kit	For motor/ integrated drive	Ambient temperature [°C]	Part No.	Type
EADS-F-40P	EAMM-U-50-D32-40P-78-S1	EMME-AS-40	-25 ... +60	2481475	EADS-F-40P
EADS-F-60P	EAMM-U-70-D32-60P-96-S1 EAMM-U-70-D40-60P-96-S1	EMMT-AS-60, EMME-AS-60	-25 ... +60	2481479	EADS-F-60P
EADS-F-80P	EAMM-U-86-D40-80P-102-S1 EAMM-U-86-D50-80P-102-S1 EAMM-U-86-D60-80P-102-S1	EMME-AS-80	-25 ... +60	2481481	EADS-F-80P
EADS-F-100A	EAMM-U-110-D50-100A-120-S1 EAMM-U-110-D60-100A-120-S1 EAMM-U-110-D80-100A-120-S1	EMME-AS-100	-25 ... +60	2481483	EADS-F-100A
EADS-F-40A	EAMM-U-50-D32-40A-78-S1	EMMS-AS-40	-25 ... +60	2481474	EADS-F-40A
EADS-F-55A	EAMM-U-60-D32-55A-91-S1 EAMM-U-60-D40-55A-91-S1	EMMS-AS-55	-25 ... +60	2481477	EADS-F-55A
EADS-F-70A	EAMM-U-70-D32-70A-96-S1 EAMM-U-70-D40-70A-96-S1 EAMM-U-86-D40-70A-102-S1 EAMM-U-86-D60-70A-102-S1	EMMS-AS-70	-25 ... +60	2481480	EADS-F-70A
EADS-F-100A	EAMM-U-110-D50-100A-120-S1 EAMM-U-110-D60-100A-120-S1 EAMM-U-110-D80-100A-120-S1	EMMS-AS-100	-25 ... +60	2481483	EADS-F-100A
EADS-F-140A	EAMM-U-145-D80-140A-188-S1 EAMM-U-145-D100-140A-188-S1	EMMS-AS-140	-25 ... +60	2481484	EADS-F-140A
EADS-F-42A	EAMM-U-50-D32-42A-78-S1	EMMS-ST-42	-25 ... +60	2481476	EADS-F-42A
EADS-F-57A	EAMM-U-60-D32-57A-91-S1 EAMM-U-60-D40-57A-91-S1	EMMS-ST-57	-25 ... +60	2481478	EADS-F-57A
EADS-F-87A	EAMM-U-86-D40-87A-102-S1 EAMM-U-86-D50-87A-102-S1 EAMM-U-86-D60-87A-102-S1	EMMS-ST-87	-25 ... +60	2481482	EADS-F-87A
EADS-F-67A	EAMM-U-60-D32-67A-91-S1 EAMM-U-60-D40-67A-91-S1	EMCA-67	-25 ... +60	1529479	EADS-F-67A/B

Parallel kits EAMM-U-...-V/T

Type codes




		EAMM	–	U	–	45	–	V25	–	42A	–	63
Type												
EAMM	Kit											
Motor placement												
U	Parallel											
Size												
Axis mechanism interface												
V20	EGSC-25											
V25	EGSC-32, ELGC-BS-32											
V32	EGSC-45, ELGC-BS-45											
T42	EGSC-60, ELGC-BS-60											
T46	ELGC-BS-80											
Motor interface												
40P	Servo motor EMME-AS-40											
60P	Servo motor EMMT-AS-60, EMME-AS-60											
80P	Servo motor EMME-AS-80											
28A	Stepper motor EMMS-ST-28											
42A	Stepper motor EMMS-ST-42											
57A	Stepper motor EMMS-ST-57											
87A	Stepper motor EMMS-ST-87											
Centre distance												

Parallel kits EAMM-U-...-V/T

Product range overview



Permissible axis/motor combinations with mini slide EGSC-BS



- The kit can be mounted in all directions
- Third-party motors can be connected. You can find out which motors are permitted from your local Festo contact or from
➔ www.festo.com/sp/eamm


Motor ¹⁾		Parallel kit	
Type		Part No.	Type
EGSC-25			
With stepper motor			
EMMS-ST-28-...		4767125	EAMM-U-30-V20-28A-44
EGSC-32			
With servo motor			
EMME-AS-40-...		4782056	EAMM-U-45-V25-40P-63
With stepper motor			
EMMS-ST-42-...		4825645	EAMM-U-45-V25-42A-63
EGSC-45			
With servo motor			
EMME-AS-40-...		4718297	EAMM-U-45-V32-40P-63
With stepper motor			
EMMS-ST-42-...		4280674	EAMM-U-45-V32-42A-63
EGSC-60			
With servo motor			
EMMT-AS-60-...		4784301	EAMM-U-65-T42-60P-87
EMME-AS-60-...		4784301	EAMM-U-65-T42-60P-87
With stepper motor			
EMMS-ST-57-...		4331535	EAMM-U-65-T42-57A-87

1) The input torque must not exceed the maximum permissible transferable torque of the parallel kit.

Parallel kits EAMM-U-...-V/T

Product range overview

Permissible axis/motor combinations with spindle axis ELGC-BS



- The kit can be mounted in all directions
- Third-party motors can be connected. You can find out which motors are permitted from your local Festo contact or from
→ www.festo.com/sp/eamm

Motor ¹⁾	Parallel kit	
Type	Part No.	Type
ELGC-BS-32		
With servo motor		
EMME-AS-40-...	4782056	EAMM-U-45-V25-40P-63
With stepper motor		
EMMS-ST-42-...	4825645	EAMM-U-45-V25-42A-63
ELGC-BS-45		
With servo motor		
EMME-AS-40-...	4718297	EAMM-U-45-V32-40P-63
With stepper motor		
EMMS-ST-42-...	4280674	EAMM-U-45-V32-42A-63
ELGC-BS-60		
With servo motor		
EMMT-AS-60-...	4784301	EAMM-U-65-T42-60P-87
EMME-AS-60-...	4784301	EAMM-U-65-T42-60P-87
With stepper motor		
EMMS-ST-57-...	4331535	EAMM-U-65-T42-57A-87
ELGC-BS-80		
With servo motor		
EMMT-AS-60-...	4824069	EAMM-U-87-T46-60P-114
EMME-AS-60-...	4824069	EAMM-U-87-T46-60P-114
EMME-AS-80-...	4822696	EAMM-U-87-T46-80P-114
With stepper motor		
EMMS-ST-87-...	4819278	EAMM-U-87-T46-87A-114

1) The input torque must not exceed the maximum permissible transferable torque of the parallel kit.

Parallel kits EAMM-U-...-V/T



Technical data

Materials:
Housing and coupling hub: Wrought aluminium alloy
Toothed belt pulley: Sintered steel
Toothed belt: Polychloroprene
Screws: Steel



General technical data							➔ Page
Type	For axis	Transferable torque [Nm]	Mass moment of inertia [kgmm ²]	Max. rotational speed [rpm]	No-load driving torque [Nm]	Weight [g]	
EAMM-U-30-V20-28A-44	EGSC	0.055	2.11	3000	0.015	97	29
EAMM-U-45-V25-40P-63	EGSC, ELGC-BS	0.5	4.35	3600	0.05	253	
EAMM-U-45-V25-42A-63	EGSC, ELGC-BS	0.5	4.35	3600	0.05	247	
EAMM-U-45-V32-40P-63	EGSC, ELGC-BS	0.5	4.35	3600	0.05	248	
EAMM-U-45-V32-42A-63	EGSC, ELGC-BS	0.5	4.35	3600	0.05	243	
EAMM-U-65-T42-57A-87	EGSC, ELGC-BS	1.8	41	3000	0.22	594	
EAMM-U-65-T42-60P-87	EGSC, ELGC-BS	1.8	41	3000	0.22	583	
EAMM-U-87-T46-60P-114	ELGC-BS	1.8	41	3000	0.22	913	
EAMM-U-87-T46-80P-114	ELGC-BS	1.8	44	3000	0.22	1140	
EAMM-U-87-T46-87A-114	ELGC-BS	1.8	41	3000	0.22	876	

Operating and environmental conditions		
Gear ratio		1:1
Ambient temperature	[°C]	0 ... +50
Storage temperature	[°C]	−20 ... +60
Degree of protection ¹⁾		IP40
Relative air humidity	[%]	0 ... 95
Corrosion resistance class CRC ²⁾		1
Note on materials		RoHS compliant

1) Only in combination with attached motor and axis.
2) Corrosion resistance class CRC 1 to Festo standard FN 940070
Low corrosion stress. For dry indoor applications or transport and storage protection. Also applies to parts behind covers, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions).

Parallel kits EAMM-U-...-V/T

Technical data

FESTO

Dimensions and ordering data

Download CAD data → www.festo.com

EGSC-BS, ELGC-BS...




Illustration:

- 1 Parallel kit
- 2 Mini slide, spindle axis
- 3 Motor

Type	B1	H1	H2	H3	L1	L2	L3	Part No.	Type
EAMM-U-30-V20-28A-44	30	76	44	15	19.2	8.1	0.6	4767125	EAMM-U-30-V20-28A-44
EAMM-U-45-V25-40P-63	45	111	63	22.5	25	5	0.7	4782056	EAMM-U-45-V25-40P-63
EAMM-U-45-V25-42A-63						4		4825645	EAMM-U-45-V25-42A-63
EAMM-U-45-V32-40P-63						5		4718297	EAMM-U-45-V32-40P-63
EAMM-U-45-V32-42A-63						4		4280674	EAMM-U-45-V32-42A-63
EAMM-U-65-T42-57A-87	65	155	87	31	34	1	1.2	4331535	EAMM-U-65-T42-57A-87
EAMM-U-65-T42-60P-87						2.5		4784301	EAMM-U-65-T42-60P-87
EAMM-U-87-T46-60P-114	87	201.5	114	39.5	34	3	1.8	4824069	EAMM-U-87-T46-60P-114
EAMM-U-87-T46-80P-114						19.2		4822696	EAMM-U-87-T46-80P-114
EAMM-U-87-T46-87A-114						2.5		4819278	EAMM-U-87-T46-87A-114

Parallel kits EAMM-U-E/-D

Type codes




		EAMM	–	U	–	E32	–	40A
Type								
EAMM	Kit							
Motor placement								
U	Parallel							
Axis mechanism interface								
D32	EGSL-45							
D40	EGSL-55							
E32	DGE-25-SP							
E48	DGE-40-SP							
Motor interface								
40A	Servo motor EMMS-AS-40							
55A	Servo motor EMMS-AS-55							
70A	Servo motor EMMS-AS-70							

Parallel kits EAMM-U-E/-D

Product range overview



Permissible axis/motor combinations with spindle axis DGE-SP



- The kit can be mounted in all directions


Motor	Parallel kit	
Type	Part No.	Type
DGE-25		
With servo motor		
EMMS-AS-55-...	543230	EAMM-U-E32-55A
DGE-40		
With servo motor		
EMMS-AS-70-...	543234	EAMM-U-E48-70A

Parallel kits EAMM-U-E/-D

Product range overview



Permissible axis/motor combinations with mini slide EGSL



- The kit can only be mounted at the side and underneath

Motor Type	Parallel kit	
	Part No.	Type
EGSL-45		
With servo motor		
EMMS-AS-40-...	543150	EAMM-U-D32-40A
EGSL-55		
With servo motor		
EMMS-AS-55-...	543157	EAMM-U-D40-55A

Parallel kits EAMM-U-E/-D

Technical data

Materials:

Housing: Gravity die-cast aluminium

Clamping component, clamping sleeve, toothed belt pulley:

Corrosion-resistant steel

Toothed belt: Polychloroprene

Screws: Galvanised steel



General technical data							
Type	For axis	Transferable torque [Nm]	Mass moment of inertia [kgmm ²]	Max. rotational speed [rpm]	No-load driving torque [Nm]	Weight [g]	→ Page
EAMM-U-D32-40A	EGSL	1	2.93	6000	0.05	300	34
EAMM-U-D40-55A	EGSL	3	10.0	5000	0.1	530	
EAMM-U-E32-55A	DGE-SP	3	10.2	3000	0.1	540	
EAMM-U-E48-70A	DGE-SP	5.5	71.1	3000	0.3	1300	

Operating and environmental conditions		
Gear ratio		1:1
Ambient temperature	[°C]	0 ... +50
Storage temperature	[°C]	-25 ... +60
Degree of protection ¹⁾		IP40
Relative air humidity	[%]	0 ... 95
Corrosion resistance class CRC ²⁾		1
Note on materials	Contains paint-wetting impairment substances	
	RoHS compliant	

1) Only in combination with attached motor and axis.

2) Corrosion resistance class CRC 1 to Festo standard FN 940070

Low corrosion stress. For dry indoor applications or transport and storage protection. Also applies to parts behind covers, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions).

Parallel kits EAMM-U-E/-D

Technical data



Dimensions and ordering data

Download CAD data → www.festo.com

DGE-SP...

Technical drawing of the parallel kit assembly. The top view shows a rectangular base with four mounting holes, with dimensions B1 (width) and H1 (height). The side view shows the assembly with dimensions L1 (width of the main body), L2 (width of the base), L3 (total width), H2 (height of the main body), and H3 (height of the base). Callouts 1, 2, and 3 point to the parallel kit, spindle axis, and motor respectively.

Illustration:

- 1 Parallel kit
- 2 Spindle axis
- 3 Motor

Type	B1	H1	H2	H3	L1	L2	L3	Part No.	Type
EAMM-U-E32-55A	56.4	132.7	76.5 ₋₀₁	28.2	47	53.5	–	543230	EAMM-U-E32-55A
EAMM-U-E48-70A	85.8	189.9	107.5 ₋₀₂	42.9	58	66.5	–	543234	EAMM-U-E48-70A

Parallel kits EAMM-U-E/-D

Technical data



Dimensions and ordering data

Download CAD data → www.festo.com

EGSL-...

1 Parallel kit
2 Spindle axis
3 Motor

Note
The kit can only be mounted at the side and underneath

Type	B1	H1	H2 ±0.1	H3	L1	L2	Part No.	Type
EAMM-U-D32-40A	45.1	93.1	48	22.6	40	4	543150	EAMM-U-D32-40A
EAMM-U-D40-55A	56.5	115	60	28.2	47	4	543157	EAMM-U-D40-55A

Festo - Your Partner in Automation



1 Festo Inc.
5300 Explorer Drive
Mississauga, ON L4W 5G4
Canada

Festo Customer Interaction Center

Tel: 1 877 463 3786
Fax: 1 877 393 3786
Email: customer.service.ca@festo.com



2 Festo Pneumatic
Av. Ceylán 3,
Col. Tequesquináhuac
54020 Tlalnepanla,
Estado de México

Multinational Contact Center

01 800 337 8669
ventas.mexico@festo.com



3 Festo Corporation
1377 Motor Parkway
Suite 310
Islandia, NY 11749

Festo Customer Interaction Center

1 800 993 3786
1 800 963 3786
customer.service.us@festo.com



4 Regional Service Center
7777 Columbia Road
Mason, OH 45040

Connect with us



www.festo.com/socialmedia



www.festo.com

Subject to change