Planar surface gantries EXCM

FESTO



At a glance

General

- A gantry that is characterised by excellent functionality in compact installation spaces
- The drive concept has a low moving mass
- Perfectly matched drive and controller package
- The kinematics are actuated via 2 stepper motors with integrated optical encoder (closed loop) and a suitable two-axis controller
- Can be actuated using two operating modes:
 - Direct mode via Ethernet and CAN
 - Record selection via digital I/O, Ethernet and CAN
- Flexible motor mounting possible


Application examples

- Feeding, pressing, joining components
- Dispensing liquid media
- Mounting electronic components

EXCM-30





EXCM-40




Functional principle

A slide is moved in a two-dimensional space (X-axis/Y-axis) via a toothed belt. The system is powered via 2 fixed motors in position-controlled operation (closed loop). The motors are coupled to the toothed belt. The belt is guided by pulleys so that the slide can move to any position in a working space when the motors are actuated.








| Planar surface gantry | | | | | |
|---|------|---|----------------------------------|--|--|
| Туре | | EXCM-30 | EXCM-40 | | |
| Guide | | Recirculating ball bearing guide | Recirculating ball bearing guide | | |
| Stroke of the | | | | | |
| X-axis | [mm] | 100, 150, 200, 300, 400, 500 | - | | |
| Y-axis [mm] | | 90 700 | 200 2000 | | |
| | | 110, 160, 210, 260, 310, 360, 410, 460, 510 | - | | |
| | | 110 510 | 200 1000 | | |
| Rated load at max. dynamic response ¹⁾ | [kg] | 2/3 ²⁾ | 4 | | |
| Repetition accuracy | [mm] | ±0.05 | ±0.1 | | |
| Mounting position | | Any | Horizontal | | |
| Controller | | Separate | Separate | | |
| Additional technical data | | → Page 8 | → Page 22 | | |

- 1) Rated load = tool load (attachment components) + payload
- 2) Vertical/horizontal mounting position

| Controller | | | | | |
|---|--------|--|---------|--|--|
| For planar surface gantry | | EXCM-30 | EXCM-40 | | |
| Can be ordered via modular product system | EXCMPF | | | | |
| Load supply | [V DC] | 48 or 24 | 48 | | |
| Nominal current [A] | | 10 | | | |
| Switching logic | | PNP | | | |
| Safety function to EN 61800-5-2 | , | Safe torque off (STO) | | | |
| Configuration support | | FCT (Festo Configuration Tool) with plug-in CMXH | | | |
| Technical data | | → Internet: cmxh | | | |

FCT software - Festo Configuration Tool

Software platform for electric drives from Festo



- All drives in a system can be managed and saved in a common project
- $\bullet \;\;$ Project and data management for all supported types of equipment
- Simple to use thanks to graphically-supported parameter entry
- Universal mode of operation for all drives
- Work offline at your desk or online at the machine


Record table

- 31 records ensure flexible positioning
- The following parameters can be set flexibly for each application:
 - Position
 - Speed
 - Acceleration
 - Jerk (only with controller CMXH)
- Absolute or relative positioning values can be used
- Complete performance test


EXCM-30 – Motor mounting variants

Underneath

EXCM-30-...-B1 – Cable outlet to the front




EXCM-30-...-B3 - Cable outlet on the inside




Additional technical data → page 8

EXCM-30-...-B2 – Cable outlet to the rear




EXCM-30-...-B4 – Cable outlet on the outside




EXCM-30 - Motor mounting variants

n ton


EXCM-30-...-T1 – Cable outlet to the front




EXCM-30-...-T3 – Cable outlet on the inside



EXCM-30-...-T2 – Cable outlet to the rear




EXCM-30-...-T4 – Cable outlet on the outside




EXCM-40 – Motor mounting variants

Additional technical data → page 22 EXCM-40-...-B – Motor underneath



EXCM-40-...-T – Motor on top




Type codes

| 001 | Series | |
|------|-----------------------------------|--|
| EXCM | Planar surface gantry | |
| 002 | Size | |
| | | |
| 30 | 30 | |
| 40 | 40 | |
| 003 | Stroke of the X-axis [mm] | |
| | 90 2000 | |
| 004 | Stroke of the Y-axis [mm] | |
| | 110 1000 | |
| Loor | Louis | |
| 005 | Guide | |
| KF | Recirculating ball bearing guide | |
| 006 | Motor type | |
| W | Without motor | |
| ST | Stepper motor ST | |
| SB | Stepper motor ST with brake | |
| 007 | Protection against particles | |
| | Standard | |
| P8 | Protected version | |
| 008 | Motor attachment position | |
| В | Underneath | |
| B1 | Underneath, cable outlet at front | |
| B2 | Underneath, cable outlet at rear | |
| В3 | Underneath, cable outlet internal | |
| B4 | Underneath, cable outlet external | |
| T | Тор | |
| T1 | Top, cable outlet at front | |
| T2 | Top, cable outlet at rear | |
| T3 | Top, cable outlet internal | |
| T4 | Top, cable outlet outside | |

| 009 | Controller | |
|----------------------------|---------------------------------------|--------------|
| | None | |
| E | Offset, NPN (24 V) | † |
| PF | Offset, PNP (24/48 V) | |
| 010 | Cable length | |
| | None | Τ |
| 2 | 0.5 m | T |
| 3 | 1 m | T |
| 4 | 1.5 m | T |
| 5 | 2 m | T |
| 6 | 5 m | |
| 7 | 10 m | |
| 011 | Attachment components | |
| 011 | None | |
| P1 | Pneumatic lifting unit, stroke 50 mm | T |
| P2 | Pneumatic lifting unit, stroke 100 mm | Ť |
| Р3 | Pneumatic lifting unit, stroke 150 mm | Ť |
| HE1 | Electric lifting unit, stroke 100 mm | |
| 012 | Mounting kit | |
| | With mounting component | Т |
| J | With adjusting kit | T |
| 013 | Document language | |
| DE | German | |
| | English | Ť |
| EN | 2.13.13.1 | |
| | Spanish | T |
| ES | - | |
| ES FR | Spanish | |
| EN ES FR IT RU | Spanish French | |
| ES FR IT | Spanish French Italian | |


Peripherals overview



Variants and accessories


[1] With protection against particles EXCM-...-P8

The cover protects the guide of the Y-axis against contamination.



[2] With adjusting kit EADC-E11

With the adjusting kit, the gantry can be aligned after installation.



Peripherals overview

| Acce | Accessories | | | | |
|------|--|---|-----------------|--|--|
| Туре | | Description | → Page/Internet | | |
| [1] | Profile mounting MUE | Included in the scope of delivery of the planar surface gantry: • X-stroke < 500 mm: 2 pairs • X-stroke ≥ 500 mm: 3 pairs | 39 | | |
| [2] | Sensor mounting EAPR | For homing in combination with third-party motors | 41 | | |
| [3] | Proximity switch SIES-8M | | 45 | | |
| [4] | Drive package comprising: controller, motor, motor cable | Available with or without drive package | 20 | | |
| [5] | Control cable NEBC-S1H15 | For the I/O interface to any controller | 46 | | |
| [6] | Plug | Included in the scope of delivery of the drive package | - | | |
| [7] | Energy chain EADH-U-3D | For routing the cables for the Z-axis | 42 | | |
| [8] | Connection set | Holder for mounting the energy chain Included in the scope of delivery: 2 terminal fittings 4 socket head screws M4x10 | 42 | | |
| [9] | Mounting kit EAHT-E9 | Mounting kit for the energy chain and a Z-axis, such as EGSL, DGSL, EGSK Stroke reduction in combination with mounting kit EAHT → page 15 | 40 | | |
| [10] | Adjusting kit EADC-E11 | Height-adjustable mounting kit | 39 | | |
| [11] | H-rail mounting CAFM-D3 | For mounting the controller on an H-rail to EN 50022 | 44 | | |

- 📱 - Note

Homing is always carried out using the mechanical stop in combination with the drive package from Festo; the sensor mounting and proximity switch are not required in this case.



| General technical data | | | |
|---|---------------------|---|--|
| Design | | Planar surface gantry | |
| Guide | | Recirculating ball bearing guide | |
| Stroke of the | | | |
| X-axis | [mm] | 100, 150, 200, 300, 400, 500 | |
| | | 90 700 | |
| Y-axis | [mm] | 110, 160, 210, 260, 310, 360, 410, 460, 510 | |
| | | 110 510 | |
| Rated load at max. dynamic response ¹⁾ | [kg] | 2/3 ²⁾ | |
| Max. process force ³⁾ | [N] | 100 | |
| Max. torque | | → Page 12 | |
| Max. no-load torque | | → Page 12 | |
| Nominal torque of motor [Nm] | | 0.5 | |
| Motor holding torque [Nm] | | 0.5 | |
| Max. acceleration | | | |
| EXCMPF | [m/s ²] | 20/10 ⁴⁾ | |
| Max. speed | | | |
| EXCMSBPF | [m/s] | 0.5 | |
| EXCMSTPF | [m/s] | 1.0/0.5 ⁴⁾ | |
| Repetition accuracy [mm] | | ±0.05 | |
| Mounting position | | Any ⁵⁾ | |
| Type of mounting | | | |
| Planar surface gantry | | With profile mounting | |
| Controller | | Via H-rail, on sub-base | |

- 1) Rated load = tool load (attachment components) + payload
- $2) \quad \mbox{ Vertical/horizontal mounting position.}$
- Perpendicular to working plane, at standstill
- 4) In case of a load supply of 48 V/24 V
- 5) Motors with brake must be used in the case of vertical mounting

| Operating and environmental conditions | | | |
|--|---------|---------------------------|--|
| Degree of protection | | IP20 | |
| Ambient temperature | [°C] | +10 +45 | |
| Storage temperature | [°C] | -10 +60 | |
| Relative humidity | [%] | 0 90 (non-condensing) | |
| Sound pressure level | [dB(A)] | 52 | |
| Duty cycle | [%] | 100 | |
| CE marking (see declaration of conformity) | | To EU Machinery Directive | |




- Note

Technical data for controller

→ Internet: cmxh

Materials



| Size | | 30 | |
|------|-------------------|--|--|
| [1] | Guide pulley | Aluminium | |
| [2] | Toothed belt | Polychloroprene with glass cord | |
| [3] | Cover | | |
| | X-axis | Polymer | |
| | Y-axis | Stainless steel | |
| [4] | Slide | Aluminium | |
| [5] | End cap | Aluminium | |
| [6] | Y-axis | Aluminium | |
| - | Guide | Steel | |
| | Ball bearings | Steel | |
| | Note on materials | RoHS-compliant | |
| | | Contains paint-wetting impairment substances | |


| Weight [kg] | | |
|---|-----------------------------------|--|
| Product weight with 0 mm stroke (without ra | ted load, motors and controllers) | |
| EXCM | 1.73 | |
| EXCMP8 | 1.80 | |
| Y-axis (without slide) | 0.34/0.4 ¹⁾ | |
| Additional weight per 50 mm stroke | | |
| X-axis | 0.237 | |
| Y-axis | 0.120/0.1321) | |
| Weight | | |
| 2 motors | 0.9 | |
| 2 motors with brake | 1.5 | |
| Controller | 0.65 | |

¹⁾ Standard/with protection against particles P8

Acceleration a as a function of the rated load m and stroke of the Y-axis

The following data applies to a horizontal mounting position and refers to the service life of the mechanical system of 3500 km. For vertical mounting positions, please get in touch with your local contact at Festo.

The centre of gravity of the slide is at the height of the slide in the Z-direction and in the centre of the slide in the X-/Y-directions.



| Stroke, Y-axis = 110/160/210 mm |
|---------------------------------|
| Stroke, Y-axis = 260 mm |
| Stroke, Y-axis = 310 mm |
| Stroke, Y-axis = 360 mm |
| Stroke, Y-axis = 410 mm |
| Stroke, Y-axis = 460 mm |
| Stroke, Y-axis = 510 mm |


Torque M as a function of rotational speed n

Typical motor characteristic curve with nominal voltage and optimal controller.


In combination with:

EXCM-...-ST-...-PF (for 24 V)


EXCM-...-SB-...-PF (for 48 V)



In combination with: EXCM-...-ST-...-PF (for 48 V)



No-load torque M as a function of rotational speed n



Characteristic load values

The centre of gravity of the slide is at the height of the slide in the Z-direction and in the centre of the slide in the X-/Y-directions.

The system is subject to the greatest load in the case of 45° travel.

The following data apply in this case:

Formula for calculating the required torque M and the required rotational speed n

$$M_{45^{\circ}}$$
 = a x (4.28 x m_L + 2.14 x m_{Ay} + 23.38 x J_m + 0.56) x 10^{-3} + M_R

 $n_{45^{\circ}} = 2232 \,\mathrm{x}\,\mathrm{v}$

 $a = acceleration [m/s^2]$

v = speed [m/s]

 $m_{Ay} = product weight of the Y-axis [kg] \rightarrow page 11$

m_L = attachment component (Z-axis) [kg] with payload

 $J_m = moment of inertia of the motor [kgcm²] \rightarrow table below$

 $M_R = \text{no-load torque [Nm]} \rightarrow \text{page } 12$

n_{45°} = rotational speed at 45° travel [rpm]

| Combination of planar surface gantry with stepper motor for X-/Y-axis | | | | |
|---|------------|------------------------------------|--|--|
| Planar surface gantry | Motor | Moment of inertia of motor [kgcm²] | | |
| EXCM-30ST | EMMS-ST-42 | 0.082 | | |
| EXCM-30SB | EMMS-ST-42 | 0.095 | | |

Sample calculation


Assuming:

Planar surface gantry EXCM-30-700-410-KF-ST

 $a_{max} = 10 \text{ m/s}^2$

 $v_{max} = 2 \text{ m/s}$

Payload = 0.5 kg



Calculation:

1. What is the max. acceleration permitted by the mechanical system?

Moving mass m_L on the Y-axis:

 $m_L = 2 \text{ kg}$


Stroke of the Y-axis:

410 mm

Result:

With a moving mass m_L of 2 kg, the maximum permissible acceleration

The required acceleration of 10 m/s^2 is therefore permissible.



Stroke, Y-axis = 110/160/210 mm Stroke, Y-axis = 260 mm Stroke, Y-axis = 310 mm Stroke, Y-axis = 360 mm Stroke, Y-axis = 410 mm

--- Stroke, Y-axis = 460 mm

- Stroke, Y-axis = 510 mm



The following data applies to a horizontal mounting position. For a vertical mounting position, please get in touch with your local contact at Festo.

The centre of gravity of the slide is at the height of the slide in the Z-direction and in the centre of the slide in the X-/Y-directions.

Sample calculation

2. Is the attached motor sufficient for this load?

Assuming: $M_{45^{\circ}} = a \times (4.28 \times m_L + 2.14 \times m_{Ay} + 23.38 \times J_m + 0.56) \times 10^{-3} + M_R$

 $a_{max} = 10 \text{ m/s}^2$ $n_{45^{\circ}} = 2232 \text{ x v}$ $v_{max} = 0.35 \text{ m/s}$

 $\begin{array}{lll} v_{max} &= 0.35 \text{ m/s} \\ m_{Ay} &= 1.32 \text{ kg} & a = & acceleration [m/s^2] \\ m_{L} &= 2 \text{ kg} & v = & speed [m/s] \end{array}$

 $J_m = 0.082 \text{ kgcm}^2$ $m_{Ay} = \text{ product weight of the Y-axis [kg]} \rightarrow \text{page } 11$ $m_1 = \text{ attachment component (Z-axis) [kg] with payload}$


 $J_m = moment of inertia of the motor [kgcm²] \rightarrow table below$

 $M_R = \text{no-load torque [Nm]} \rightarrow \text{page } 12$

n_{45°} = nominal rotational speed at 45° travel [rpm]

Determining M45°

 $n_{45^{\circ}}$ = 2232 x 0.35 ms = 781.2 rpm




No-load torque:

EXCM-30

 $M_R = 0.12 \text{ Nm}$

 $M_{45^{\circ}}$ = a x (4.28 x m_L + 2.14 x m_{Ay} + 23.38 x J_m + 0.56) x 10^{-3} + M_R

 $M_{45^{\circ}} = 10 \text{ m/s}^2 \text{ x} (4.28 \text{ x 2 kg} + 2.14 \text{ x } 1.32 \text{ kg} + 23.38 \text{ x } 0.082 \text{ kgcm}^2 + 0.56) \text{ x } 10^{-3} + 0.12 \text{ Nm} = 0.26 \text{ Nm}$ Result:



The value for the torque lies below the motor characteristic curve.

The design is thus acceptable.




Note

These requirements for the dynamic response apply to 45° travel.
The dynamic values may be higher for travel only in the X- or Y-direction.

Minimum number of profile mountings


Different numbers of profile mountings must be used as a function of the mounting position and stroke of the X-axis.




Stroke reduction in combination with mounting kit EAHT-E9

The reduction is influenced by the following factors:


- [1] The mounting kit EAHT-E9 is wider than the slide of the Y-axis
- [2] By adjusting kits EADC-E11 or profile mountings MUE that are mounted on the inside of the X-axis
- [3] By using an additional mounting surface for the cover in combination with EXCM-...-P8 (with protection against particles)





| | B3 (→ fro | m page 16) | L | | |
|--|-------------|-------------|----------|---------------------|--|
| | For EXCM | For EXCMP8 | For EXCM | For EXCMP8 | |
| With mounting kit EAHT-E9 | 38 + stroke | 63 + stroke | 2x 8 mm | No stroke reduction | |
| With mounting kit EAHT-E9 and | | | 2x 16 mm | 2x 4 mm | |
| adjusting kits EADC-E11/ profile mountings | | | | | |
| MUE | | | | | |

Dimensions Download CAD data → www.festo.com EXCM-30-... and EXCM-30-...-P8 Motor attachment position – Underneath 2 2 £ Ξ 3-В2 L3 L4 1 B4 B3 B1 L8 L1 [1] Transport lock serves as transport aid and can be removed after assembly [2] Threaded pin for securing the adjusting screws [3] Screw for setting the toothed belt tension Motor interface Coupling interface Coupling interface with radial threaded pins with tangential clamping screws



| Туре | B5 | B6 | B7 | B8 | D1 | D2 | D3 | D4 | D5 |
|-----------|--------|--------|--------|--------|------|------|-----|------|-------|
| | | | | | Ø | Ø | Ø | Ø | |
| | | ±0.03 | | ±0.1 | H7 | | f8 | H8 | |
| EXCM-30 | 38 | 26 | 42 | 31 | 22 | 16 | 5 | 5 | M4 |
| EXCM-30P8 | 38 | 26 | 42 | 31 | 22 | 16 | 5 | 5 | M4 |
| _ | 1 | | 1 | | 1 | 1 | 1 | 1 | 1 |
| Туре | | H1 | _ | H2 | H3 | H4 | H5 | L3 | L4 |
| | EXCMST | EXCMSB | EXCMST | EXCMSB | | | | | |
| | | | ±0.7 | | | | | | ±0.03 |
| EXCM-30 | 129.2 | 186.2 | 124.2 | 181.2 | 53.8 | 54 | 5 | 60 | 42 |
| EXCM-30P8 | 131.2 | 188.2 | 124.2 | 181.2 | 53.8 | 56 | 7 | 60 | 42 |
| _ | 1 | 1 | 1 | 1 | 1 | l =- | 1 | l | 1 |
| Туре | L5 | L6 | L7 | L8 | T1 | T2 | T3 | T4 | T5 |
| | | ±0.1 | | | | | | | |
| EXCM-30 | 42 | 31 | 20 | 5.6 | 3 | 26 | 3.7 | 28.7 | 24.5 |
| EXCM-30P8 | 42 | 31 | 20 | 5.6 | 3 | 26 | 3.7 | 28.7 | 24.5 |

| Stroke-dependent dimensions | | |
|-----------------------------|--------------|---------------|
| Stroke of the X-axis | L1 | L2 |
| | | ±0.2 |
| 100 | 233 | 150.5 |
| 150 | 283 | 200.5 |
| 200 | 333 | 250.5 |
| 300 | 433 | 350.5 |
| 400 | 533 | 450.5 |
| 500 | 633 | 550.5 |
| 90 700 | 133 + stroke | 50.5 + stroke |

| Stroke of the | B | B1 | | 32 | B3 | | B4 | |
|---------------|--------------|--------------|--------------|--------------|-------------|-------------|-------------|-------------|
| Y-axis | EXCM- | ·30 | 30 EXCM- | | EXCM- | 30 | EXCM- | 30 |
| | | P8 | | P8 | | P8 | | P8 |
| 110 | 240 | 265 | 232 | 257 | 148 | 173 | 140 | 165 |
| 160 | 290 | 315 | 282 | 307 | 198 | 223 | 190 | 215 |
| 210 | 340 | 365 | 332 | 357 | 248 | 273 | 240 | 265 |
| 260 | 390 | 415 | 382 | 407 | 298 | 323 | 290 | 315 |
| 310 | 440 | 465 | 432 | 457 | 348 | 373 | 340 | 365 |
| 360 | 490 | 515 | 482 | 507 | 398 | 423 | 390 | 415 |
| 410 | 540 | 565 | 532 | 557 | 448 | 473 | 440 | 465 |
| 460 | 590 | 615 | 582 | 607 | 498 | 523 | 490 | 515 |
| 510 | 640 | 665 | 632 | 657 | 548 | 573 | 540 | 565 |
| 110 510 | 130 + stroke | 155 + stroke | 122 + stroke | 147 + stroke | 38 + stroke | 63 + stroke | 30 + stroke | 55 + stroke |

Dimensions Download CAD data → www.festo.com EXCM-30-... and EXCM-30-...-P8 Motor attachment position – On top D4 Į 꿈 2 £ 2 L4 B B2 1 B4 B3 B1 L2 <u>L8</u> L1 [1] Transport lock serves as transport aid and can be removed after assembly [2] Threaded pin for securing the adjusting screws [3] Screw for setting the toothed belt tension Motor interface Coupling interface Coupling interface with radial threaded pins with tangential clamping screws

| Туре | B5 | B6 | B7 | B | 8 | D1 | D2 | | D3 | D4 |
|-----------|----|--------|--------|-----|----|----|-----|-----|------|-------|
| | | | | | | Ø | Ø | | Ø | Ø |
| | | ±0.03 | | ±0 | .1 | H7 | | | f8 | H8 |
| EXCM-30 | 38 | 26 | 42 | 3: | 1 | 22 | 16 | | 5 | 5 |
| EXCM-30P8 | 38 | 26 | 42 | 3: | 1 | 22 | 16 | | 5 | 5 |
| | 1 | 1 | | 1 | 1 | | 1 | | | |
| Туре | D5 | | H2 | H; | 3 | H4 | H5 | | L3 | L4 |
| | | EXCMST | EXCMSB | | | | | | | |
| | | ±1 | | | | | | | | ±0.03 |
| EXCM-30 | M4 | 146.2 | 203.2 | 75 | .6 | 54 | 5 | | 60 | 42 |
| EXCM-30P8 | M4 | 146.2 | 203.2 | 75 | .6 | 56 | 7 | | 60 | 42 |
| 1 | | | | | 1 | 1 | - 1 | | | 1 |
| Туре | L5 | L6 | L7 | L8 | T1 | T2 | | T3 | T4 | T5 |
| | | | | | | | | | | |
| | | ±0.1 | | | | | | | | |
| EXCM-30 | 42 | 31 | 20 | 5.6 | 3 | 26 | , | 3.7 | 28.7 | 24.5 |
| EXCM-30P8 | 42 | 31 | 20 | 5.6 | 3 | 26 | 5 | 3.7 | 28.7 | 24.5 |

| Stroke-dependent dimen | sions | |
|-------------------------|--------------|---------------|
| Stroke of the X-axis | L1 | L2 |
| | | ±0.2 |
| 100 | 233 | 150.5 |
| 150 | 283 | 200.5 |
| 200 | 333 | 250.5 |
| 300 | 433 | 350.5 |
| 400 | 533 | 450.5 |
| 500 | 633 | 550.5 |
| 90 700 | 133 + stroke | 50.5 + stroke |

| Stroke of the | B | B1 | | 32 | B3 | | B4 | |
|---------------|--------------|--------------|--------------|--------------|-------------|-------------|-------------|-------------|
| Y-axis | EXCM- | ·30 | 30 EXCM- | | EXCM- | 30 | EXCM- | 30 |
| | | P8 | | P8 | | P8 | | P8 |
| 110 | 240 | 265 | 232 | 257 | 148 | 173 | 140 | 165 |
| 160 | 290 | 315 | 282 | 307 | 198 | 223 | 190 | 215 |
| 210 | 340 | 365 | 332 | 357 | 248 | 273 | 240 | 265 |
| 260 | 390 | 415 | 382 | 407 | 298 | 323 | 290 | 315 |
| 310 | 440 | 465 | 432 | 457 | 348 | 373 | 340 | 365 |
| 360 | 490 | 515 | 482 | 507 | 398 | 423 | 390 | 415 |
| 410 | 540 | 565 | 532 | 557 | 448 | 473 | 440 | 465 |
| 460 | 590 | 615 | 582 | 607 | 498 | 523 | 490 | 515 |
| 510 | 640 | 665 | 632 | 657 | 548 | 573 | 540 | 565 |
| 110 510 | 130 + stroke | 155 + stroke | 122 + stroke | 147 + stroke | 38 + stroke | 63 + stroke | 30 + stroke | 55 + stroke |

Ordering data – Modular product system

| Ordering table | | | 1 | | 1 |
|------------------------------|------|--|------------|------|------------|
| Size | | 30 | Conditions | Code | Enter code |
| Module no. | | 2226101 | | | |
| Product type | | EXCM series M | | EXCM | EXCM |
| Size | | 30 | | -30 | 30 |
| Stroke of the | [mm] | 100 | | -100 | |
| X-axis | [mm] | 150 | | -150 | |
| | [mm] | 200 | | -200 | |
| | [mm] | 300 | | -300 | |
| | [mm] | 400 | | -400 | |
| | [mm] | 500 | | -500 | |
| | [mm] | 90 700 | | | |
| Stroke of the | [mm] | 110 | | -110 | |
| Y-axis | [mm] | 160 | | -160 | |
| | [mm] | 210 | | -210 | |
| | [mm] | 260 | | -260 | |
| | [mm] | 310 | | -310 | |
| | [mm] | 360 | | -360 | |
| | [mm] | 410 | | -410 | |
| | [mm] | 460 | | -460 | |
| | [mm] | 510 | | -510 | |
| | [mm] | 110 510 | | | |
| Guide | | Recirculating ball bearing guide | | -KF | KF |
| Motor type | | Stepper motors | | -ST | |
| | | Stepper motors with brake | | -SB | |
| | | Without stepper motors | [1] | -W | |
| Protection against particles | | Standard | | | |
| | | Protected version | | -P8 | |
| Motor attachment position | | Underneath | [2] | -B | |
| | | Underneath, cable outlets to the front | | -B1 | |
| | | Underneath, cable outlets to the rear | | -B2 | |
| | | Underneath, cable outlets on the inside | | -B3 | |
| | | Underneath, cable outlets on the outside | | -B4 | |
| | | On top | [2] | -T | |
| | | On top, cable outlets to the front | | -T1 | |
| | | On top, cable outlets to the rear | | -T2 | |
| | | On top, cable outlets on the inside | | -T3 | |
| | | On top, cable outlets on the outside | | -T4 | |

^[1] W In combination with "Without stepper motors" W, controllers E and PF are not required
[2] B, T Not in combination with stepper motors ST and SB. Option if third-party motors are mounted

Ordering data – Modular product system

| Ordering table | | | | | |
|-------------------|-------------------------------|------------|------|---|------------|
| Size | 30 | Conditions | Code | | Enter code |
| Controller | None | | | | |
| | Remote, PNP (24/48 V) | | -PF | | |
| Cable length | None | | | | |
| | Motor and encoder cable 0.5 m | | 2 | | |
| | Motor and encoder cable 1 m | | 3 | | |
| | Motor and encoder cable 1.5 m | | 4 | | |
| | Motor and encoder cable 2 m | | 5 | | |
| Document language | German | | -DE | | |
| | English | | -EN | | |
| | Spanish | | -ES | l | |
| | French | | -FR | | |
| | Italian | | -IT | | |
| | Russian | | -RU | | |
| | Chinese | | -ZH | | |

Selection of attachment components

The following variants for the Z-axis can optionally be ordered using the modular product system

→ page 38:


- Without attachment component
- With pneumatic attachment component (mini slide DGSL)
- With electric attachment component (mini slide EGSL)

The drives are fully connected on delivery. Cables and tubes are routed as far as the output of the energy chain (X-axis).

EXCM-...-T0... (without attachment component)

The following are pre-installed:

- 2 compressed air supply ports for e.g. Z-axis
- Multi-pin plug distributor for bundling signals:
 - e.g. proximity switch





| Compo | nents | Number of components | | |
|-------|------------------------------------|----------------------|--|--|
| [1] | Compressed air tubing | 2 | | |
| [3] | Bulkhead fitting | 2 | | |
| [6] | Plug socket with cable | 1 | | |
| [7] | Multi-pin plug distributor (6-way) | 1 | | |
| - | Earthing cable | 2 | | |

EXCM- ... -P... (pneumatic attachment component)

The following are pre-installed:

- Solenoid valve for controlling the drive
- 1 compressed air supply port for e.g. gripper
- · Proximity switch for end position sensing
- Multi-pin plug distributor for bundling signals:
 - For mini slide DGSL:
 - 2 proximity switches
 - 1 solenoid valve
 - 3 connections available





| Comp | oonents | Number of components |
|------|------------------------------------|----------------------|
| [1] | Compressed air tubing | 2 |
| [2] | Solenoid valve | 1 |
| [3] | Bulkhead fitting | 1 |
| [4] | Mini slide DGSLY3A ¹⁾ | 1 |
| [5] | Adapter plate | 1 |
| [6] | Plug socket with cable | 1 |
| [7] | Multi-pin plug distributor (6-way) | 1 |
| [8] | Proximity switch | 2 |
| - | Earthing cable | 2 |


For EXCM-40, the mini slide DGSL-16 is used with progressive shock absorbers.
 Additional information → Internet: dgsl


Selection of attachment components

EXCM-...-HE... (electric attachment component)

The following are pre-installed:

- 2 compressed air supply ports for e.g. gripper
- Multi-pin plug distributor for bundling signals:
 - e.g. proximity switch







| Comp | onents | Number of components |
|------|------------------------------------|----------------------|
| [1] | Compressed air tubing | 2 |
| [3] | Bulkhead fitting | 2 |
| [4] | Mini slide EGSL ¹⁾ | 1 |
| [5] | Adapter plate | 1 |
| [6] | Plug socket with cable | 1 |
| [7] | Multi-pin plug distributor (6-way) | 1 |
| [9] | Parallel kit | 1 |
| [10] | Motor | 1 |
| [11] | Motor cable | 1 |
| [12] | Encoder cable | 1 |
| - | Earthing cable | 2 |

For EXCM-40, the mini slide EGSL-45 is used with a pitch of 10 mm.
 Additional information → Internet: egsl

Peripherals overview



Proximity switch for sensing the position of the slide on the Y-axis



Peripherals overview

| Туре | ttachments and accessories /pe Description | | → Page/Internet | | |
|------|---|--|-----------------|--|--|
| [1] | Controller | For controlling the planar surface gantry | cmxh | | |
| 1] | CMXH | For controlling the planar surface gantry | CIIIXII | | |
| 2] | Mini slide | Pneumatic attachment component (mini slide DGSL) for the Z-axis | 38 | | |
| .4] | P1, P2, P3 | Fileumatic attachment component (imm stude 2001) for the 2-axis | 76 | | |
| [3] | Mini slide | Electric attachment component (mini slide EGSL) with motor cable NEBM and encoder cable NEBM for the | 38 | | |
| [2] | HE1 | 7-axis | 76 | | |
| [4] | Proximity switch | For position sensing on the Z-axis | 45 | | |
| .↔] | SME-10M/SIES-8M | Included in the scope of delivery of the planar surface gantry EXCMP | 43 | | |
| [5] | Motor cable | Connecting cable between motor and controller CMXH-ST2 | 46 | | |
| [2] | NEBM | Included in the scope of delivery of the planar surface gantry EXCMST/-SB | 140 | | |
| 6] | Encoder cable | Connecting cable between encoder and controller CMXH-ST2 | 46 | | |
| ٥, | NEBM | Included in the scope of delivery of the planar surface gantry EXCMST/-SB | 140 | | |
| [7] | Sensor mounting | For mounting the proximity switches SIES-Q8B, SIES-V3B on the X-axis | 44 | | |
| , 1 | EAPR | Not included in the scope of delivery of the planar surface gantry | 1 1 1 | | |
| [8] | Proximity switch | For position sensing on the X-axis | 45 | | |
| [0] | SIES-Q8B | Not included in the scope of delivery of the planar surface gantry | " | | |
| [9] | Proximity switch | For position sensing on the X-axis | 45 | | |
| - 1 | SIES-V3B | Not included in the scope of delivery of the planar surface gantry | | | |
| 101 | Adjusting kit | Height-adjustable mounting kit for the planar surface gantry | 43 | | |
| | EADC-12 | Included in the scope of delivery of the planar surface gantry. If no adjusting kit is selected in the modular | | | |
| | | product system, the mounting kit will automatically be delivered | | | |
| [11] | Mounting kit | Non-height-adjustable mounting kit for the planar surface gantry | 43 | | |
| | EAHM-E12 | | | | |
| [12] | Multi-pin plug distributor | For connecting up to 6 inputs/outputs | nedu | | |
| | NEDU | Included in the scope of delivery of the planar surface gantry | | | |
| [13] | Plug socket with cable | Connecting cable between multi-pin plug distributor NEDU and the controller | sim | | |
| | SIM | Included in the scope of delivery of the planar surface gantry | | | |
| [14] | Energy chain | For EXCM-40: type IGUS 2500.03.075.0 | - | | |
| | | | | | |
| [15] | Plastic tubing | Two compressed air tubes are connected to the bulkhead fittings and routed in the energy chains on | pun | | |
| | PUN-H-6x1 | delivery (for pneumatic Z-axis, one tube on the valve and one on the bulkhead fitting) | | | |
| [16] | Proximity switch | For position sensing on the Y-axis | 45 | | |
| | SIES-8M | Not included in the scope of delivery of the planar surface gantry | | | |
| - | Motor cable | Connecting cable between the motor on the Z-axis and the motor controller CMMS-ST | 46 | | |
| | NEBM-S1G9 | The motor controller and connecting cable are included in the scope of delivery of the planar surface gantry | | | |
| | | EXCMHE1 | | | |
| | Encoder cable | Connecting cable between the encoder on the Z-axis and the motor controller CMMS-ST | 46 | | |
| | NEBM-M12G8 | • The motor controller and connecting cable are included in the scope of delivery of the planar surface gantry | | | |
| | | EXCMHE1 | | | |
| | One-way flow control valve | For regulating speed | 38 | | |
| | GRLA | • Included in the scope of delivery of the planar surface gantry EXCHP | | | |
| | H-rail mounting | For mounting the controller on an H-rail to EN 50022 | 44 | | |
| | CAFM-D3 | | | | |



In contrast to the X- and Y-axes, the Z-axis (with supplied controller CMMS-ST) cannot be controlled via ModBus TCP.



| General technical data | | | | | |
|--|---------------------|----------------------------------|--|--|--|
| Design | | Planar surface gantry | | | |
| Guide | | Recirculating ball bearing guide | | | |
| Stroke of the | | | | | |
| X-axis | [mm] | 200 2000 | | | |
| Y-axis | [mm] | 200 1000 | | | |
| Z-axis | [mm] | 50, 100, 150 | | | |
| EXCMHE1 | [mm] | 100 | | | |
| EXCMP1 | [mm] | 50 | | | |
| EXCMP2 | [mm] | 100 | | | |
| EXCMP3 | [mm] | 150 | | | |
| Rated load at max. dynamic response ¹⁾ [kg] | | 4 | | | |
| Process force in Z direction [N] | | 450 | | | |
| Max. torque ²⁾ | | → Page 29 | | | |
| Max. no-load torque ²⁾³⁾ | | → Page 29 | | | |
| Max. acceleration ⁴⁾ | | | | | |
| With motor and controller | [m/s ²] | → Page 29 | | | |
| Purely mechanical system | [m/s ²] | 20 | | | |
| Max. speed ⁴⁾ | | | | | |
| With motor and controller [m/s] | | 1 | | | |
| Purely mechanical system [m/s] | | 2 | | | |
| Repetition accuracy [mm] | | ±0.1 | | | |
| Mounting position | | Horizontal | | | |
| Type of mounting | | Mounting kit, adjusting kit | | | |

- 1) Rated load = tool load (attachment component (Z-axis) + e.g. gripper) + payload
- $2) \quad \text{ These values must also be complied with when installing third-party motors} \\$
- 3) At v=0.2 m/s and 45 $^{\circ}$ travel.
- 4) This data applies only under ideal conditions.
 For a precise configuration, please consult a sales engineer from Festo.
 Additional information → page 29

| Operating and environmental conditions | | | | | |
|--|---------|---------------------------|--|--|--|
| Degree of protection | | IP40 | | | |
| Ambient temperature ¹⁾ | [°C] | +10 +50 | | | |
| Storage temperature [°C] | | -10 +60 | | | |
| Relative humidity | [%] | 0 90 (non-condensing) | | | |
| Sound pressure level | [dB(A)] | 65 | | | |
| Duty cycle | [%] | 100 | | | |
| CE marking (see declaration of conformity) | | To EU Machinery Directive | | | |


1) Note operating range of proximity switches and motors



Technical data for controller

→ Internet: cmxh

Materials



| Size | | 40 | | | | |
|------|------------------------|--|--|--|--|--|
| [1] | Drive and end caps | Aluminium | | | | |
| [2] | Profiles of the X-axis | Aluminium | | | | |
| [3] | Profile of the Y-axis | Aluminium | | | | |
| [4] | Cover | | | | | |
| | X-axis | Aluminium | | | | |
| | Y-axis | Aluminium | | | | |
| [5] | Slide | Aluminium | | | | |
| - | Coupling | Aluminium with elastomer ring gear | | | | |
| | Guide | Steel | | | | |
| | Drive pinion | Steel | | | | |
| | Ball bearings | Steel | | | | |
| | Toothed belt | PU with steel cord | | | | |
| | Note on materials | RoHS-compliant RoHS-compliant | | | | |
| | | Contains paint-wetting impairment substances | | | | |

Planar surface gantries EXCM-40

Data sheet


| Weight [kg] | | | | | |
|---|------|--|--|--|--|
| Product weight with 0 mm stroke (without rated load, motors, axial kits, mounting kits) | | | | | |
| EXCMW-T | 16.7 | | | | |
| EXCMW-B | 17.5 | | | | |
| X-axis (2x) | 8.5 | | | | |
| Y-axis (without slide) | 6.2 | | | | |
| Additional weight per 100 mm stroke | | | | | |
| X-axis | 1.75 | | | | |
| Y-axis | 0.89 | | | | |
| Axial kit ¹⁾ | | | | | |
| For EMMS-ST-57-M | 0.54 | | | | |
| Motor ¹⁾ | | | | | |
| EXCMST (without brake) | 1.2 | | | | |
| EXCMSB (with brake) | 1.38 | | | | |
| Attachment component (Z-axis) | | | | | |
| Electrical | | | | | |
| EXCMHE1 | 3.3 | | | | |
| Pneumatic | | | | | |
| EXCMP1 | 1.8 | | | | |
| EXCMP2 | 2.4 | | | | |
| EXCMP3 | 2.7 | | | | |
| Mounting kit for X-axis | | | | | |
| Adjusting kit ¹⁾ | 0.78 | | | | |
| Mounting kit ¹⁾ | 0.33 | | | | |

¹⁾ Weight per component


Torque M as a function of rotational speed n

Typical motor characteristic curve with nominal voltage and optimal controller. In combination with:

EXCM-...-ST-...-PF (for 48 V) or EXCM-...-SB-...-PF (for 48 V)



No-load torque M as a function of rotational speed n



Characteristic load values

The centre of gravity of the slide is at the height of the slide in the Z-direction and in the centre of the slide in the X-/Y-directions.

The system is subject to the greatest load in the case of 45° travel.

The following data apply in this case:

Formula for calculating the required torque \boldsymbol{M} and the required rotational speed \boldsymbol{n}

$$M_{45^{\circ}} = a \, x \, (9.79 \, x \, m_L + 4.89 \, x \, m_{Ay} + 10.21 \, x \, J_m + 19.58) \, x \, 10^{-3} + M_R$$

 $n_{45^{\circ}} = 975 \,\mathrm{x}\,\mathrm{v}$

a = acceleration [m/s²]
v = speed [m/s]

 m_{Ay} = product weight of the Y-axis [kg] \rightarrow page 28

m_L = attachment component (Z-axis) [kg] with payload

 $_{m}$ = moment of inertia of the motor [kgcm²] \rightarrow table below

 $M_R = \text{no-load torque [Nm]} \rightarrow \text{page 29}$

 $n_{45^{\circ}}$ = nominal rotational speed at 45° travel [rpm]

| location of planar surface gantry to servo motor for X-/Y-axis | | | | | |
|--|---------------------|---------------------------------------|--|--|--|
| Planar surface gantry | Motor | Moment of inertia of motor [kgcm²] | | | |
| EXCM-40ST | EMMS-ST-57-M-SE-G2 | 0.48 | | | |
| EXCM-40SB | EMMS-ST-57-M-SEB-G2 | 0.5 | | | |

Sample calculation

Assuming:

Planar surface gantry

EXCM-40-1000-500-KF-SB-B-PF7-HE1-...

with attached motor


EMMS-ST-57-M-SEB-G2

 $a_{max} = 2 \text{ m/s}^2$

 $v_{max} = 0.5 \text{ m/s}$

Payload = 0.5 kg

Attachment component on Z-axis: EGSL-BS-45-100-10P



Sample calculation

2. Is the attached motor sufficient for this load?

Assuming:

 $a_{max} = 2 \text{ m/s}^2$

 $v_{max} = 0.5 \text{ m/s}$

 $m_{Ay} = 10.65 \text{ kg}$

 $m_L = 3.8 \text{ kg}$

 $J_m = 0.5 \text{ kgcm}^2$

 $\rm M_{45^{\circ}} = a~x~(9.79~x~m_L + 4.89~x~m_{Ay} + 10.21~x~J_m + 19.58)~x~10^{-3} + M_R$

 $n_{45^{\circ}} = 975 \text{ x}$

a = acceleration [m/s²]

v = speed [m/s]

 $m_{Ay} = product weight of the Y-axis [kg] \rightarrow page 28$

 $m_L = attachment component (Z-axis) [kg] with payload$

 $J_m = moment of inertia of the motor [kgcm²] \rightarrow table below$

 $M_R = \text{no-load torque [Nm]} \rightarrow \text{page } 29$

n_{45°} = nominal rotational speed at 45° travel [rpm]



Note

These requirements for the dynamic response apply to 45° travel.


The dynamic values may be higher

for travel only in the X- or Y-direction.

Sample calculation

Determining M45°

 $n_{45^{\circ}} = 975 \text{ x } 0.5 \text{ ms} = 487.5 \text{ rpm}$



No-load torque:


EXCM-40

 $M_R = 0.4 \text{ Nm}$

 $M_{45^{\circ}}$ = a x (9.79 x m_L + 4.89 x m_{Ay} + 10.21 x J_m + 19.58) x 10^{-3} + M_R

 $\mathsf{M}_{45^o} = 2~\text{m/s}^2~\text{x}~(9.79~\text{x}~3.8~\text{kg} + 4.89~\text{x}~10.65~\text{kg} + 10.21~\text{x}~0.5\text{kg}~\text{cm}^2 + 19.58)~\text{x}~10^{-3} + 0.4~\text{Nm} = 0.63~\text{Nm}$

Result:



The value for the torque lies below the motor characteristic curve.

The design is thus acceptable.

Minimum number of profile mountings


Irrespective of the mounting position, a different number of profile mountings needs to be used depending on the stroke of the X-axis.

The required number is mounted on delivery.

| Stroke of the X-axis [mm] | Number of profile mountings per axis | | | | |
|---------------------------|--------------------------------------|--|--|--|--|
| 200 499 | 2 | | | | |
| 500 899 | 2 | | | | |
| 900 1799 | 3 | | | | |
| 1800 2000 | 4 | | | | |

Distances between the profile mountings

The profile mountings must be evenly spaced by distance l.



$$l_1 = \frac{l+141}{n-1}$$

l₁ = distance


l = stroke

n = number of profile mountings per axis

Mounting position of the Z-axis

Due to manufacturing tolerances and the backlash in the guides, the angle between the X- and Z-axes may not be exactly 90° in certain circumstances. Max. deviation:

á = ±1.1°



Pin allocations

Motors on the X-/Y- and Z-axes



Encoder




| PIN | Function |
|-----|--------------|
| 1 | String A |
| 2 | String A/ |
| 3 | String B |
| 4 | String B/ |
| 5 | n. c. |
| 6 | n. c. |
| 7 | Brake (24 V) |
| 8 | Brake (0 V) |
| 9 | - |


| PIN | Function |
|-----|-----------------|
| 1 | Signal trace A |
| 2 | Signal trace A/ |
| 3 | Signal trace B |
| 4 | Signal trace B/ |
| 5 | 0 V |
| 6 | Signal trace N |
| 7 | Signal trace N/ |
| 8 | 5 V |
| | · |

Selection of cable lengths

2 cable lengths (5 m or 10 m) can be selected using the modular product system → page 38. This specification relates to the output of the energy chain at the X-axis (dimension L) and describes the minimum length by which the cables and tubing protrude. The selected length applies to the following components:

- Compressed air tubing
- Plug sockets with cable
- Motor cables
- Encoder cables
- Earthing cables





Dimensions Download CAD data → www.festo.com EXCM-40-... - Slide B15 Туре В3 В4 B5 В6 В9 B10 B11 B12 B13 B14 ±0.05 ±0.1 179.9 EXCM-40 65 65 69 56.4 41 35 30 27 106 Туре B15 D1 D2 D3 D4 D5 D6 Н1 H2 Н3 Ø Ø Ø Ø ±0.03 Н7 Н6 H7 H7 EXCM-40 12 M5 M6 Approx. 293 100.8 124/159.5¹⁾ 85 38 4 6 Туре Н4 Н5 Н6 Н7 Н8 Н9 L4 L6 L7 L8 L3 L5 EXCM-40 20 100.3 70 70 37.5 65 33.6 20 0.5 101 30.5 6 L10 L11 L12 L14 L16 T1 T2 T3 T4 Туре L13 L15 **=**©1 ±0.03 ±0.1 ±0.1 ±0.1 EXCM-40 70 46 41 44 32 18.5 12 12 6 1.9 6 Stroke-dependent dimensions Stroke of the L1 L2 L18 Stroke of the В1 B2 X-axis Y-axis

167.2+stroke

200 ... 1000

360+stroke

230+stroke

^{200 ... 2000} 1) With brake




Depending on the stroke of the X-axis, a different number of profile mountings is required. The distance between the profile mountings must always be the same (→ page 32).

382+stroke

The tension of the toothed belt must be set before commissioning. The tools required to do this (e.g. frequency meter) are not included in the scope of delivery.

→ Page 32



| Allocation of planar surface gantry to servo motor for X-/Y-axis | | | | |
|--|---------------------|--|--|--|
| Planar surface gantry | Motor | | | |
| | | | | |
| EXCM-40ST | EMMS-ST-57-M-SE-G2 | | | |
| EXCM-40SB | EMMS-ST-57-M-SEB-G2 | | | |

| Allocation of planar surface gantry to servo motor for Z-axis | | | |
|---|---------------------|--|--|
| Planar surface gantry | Motor | | |
| EXCM-40HE1 | EMMS-ST-42-S-SEB-G2 | | |



Note

Third-party motors with a driving torque that is too high can damage the planar surface gantry. When selecting the motors, please observe the limits specified in the technical data.

Ordering data – Modular product system

| Ordering table | | | | | | | |
|---------------------------|------|---------------------------------------|------------|------|-------------|--|--|
| Size | | 40 | Conditions | Code | Enter code | | |
| Module no. | | 3741955 | | | | | |
| Product type | | EXCM series M | | EXCM | EXCM -40 | | |
| Size | | 40 | | -40 | | | |
| Stroke of the X-axis | [mm] | 200 2000 | | | | | |
| Stroke of the Y-axis | [mm] | 200 1000 | | | | | |
| Guide | | Recirculating ball bearing guide | | -KF | -KF | | |
| Motor type | | Stepper motor with brake | | -SB | | | |
| | | Stepper motor | | -ST | | | |
| | | Without motor | | -W | | | |
| Motor attachment position | | Underneath | | -B | | | |
| | | On top | | -T | | | |
| Controller | | None | | | | | |
| | | Remote, PNP (48 V) | | -PF | | | |
| Cable length | | None | | | | | |
| | | 5 m | | 6 | | | |
| | | 10 m | | 7 | | | |
| Attachment components | | None | | | | | |
| | | Electric lifting unit, 100 mm stroke | | -HE1 | | | |
| | | Pneumatic lifting unit, 50 mm stroke | | -P1 | | | |
| | | Pneumatic lifting unit, 100 mm stroke | | -P2 | | | |
| | | Pneumatic lifting unit, 150 mm stroke | | -P3 | | | |
| Mounting kit | | Via mounting kit | | | | | |
| | | With adjusting kit | | -J | | | |
| Document language | | German | | -DE | | | |
| | | English | | -EN | | | |
| | | Spanish | | -ES | | | |
| | | French | | -FR | | | |
| | | Italian | | -IT | | | |
| | | Russian | | -RU | | | |
| | | Swedish | | -SV | | | |
| | | Chinese | | -ZH | | | |



In combination with key feature W (without motor), the EXCM planar surface gantry is provided without a coupling housing and without a coupling.



The planar surface gantry can only be operated with a load voltage of 48 V.

Technical data for controller

→ Internet: cmxh

Profile mounting MUE

For size 30

Material:

Anodised aluminium RoHS-compliant


For mounting the planar surface gantry (scope of delivery: 1 pair)

Included in the scope of delivery of the planar surface gantry:

X-stroke ≥ 500 mm: 3 pairs

X-stroke < 500 mm: 2 pairs





| 1 | Dimensions and ordering data | | | | | | | | | |
|---|------------------------------|----|----|----|----|-----|----|----|----|-----|
| | For size | B1 | B2 | В3 | B5 | D1 | D2 | H1 | H2 | Н3 |
| | | | | | | ø | ø | | | |
| | | | | | | | H7 | | | |
| | 30 | 58 | 8 | 50 | 4 | 3.4 | 5 | 49 | 6 | 5.5 |

| For size | H4 | H5 | L1 | L2 | Weight [g] | Part no. | Туре |
|----------|-----|----|----|----|---------------|----------|--------|
| 30 | 2.3 | 11 | 40 | 20 | 20 | 558042 | MUE-50 |


Adjusting kit EADC-E11

For size 30

Material: Anodised aluminium RoHS-compliant

For mounting and aligning the planar surface gantry. The kit is height adjustable.





| Dimensions and ord | Dimensions and ordering data | | | | | | | | | | | | |
|--------------------|------------------------------|----|---------|----|--------------|----|------|----|------|------|----|--|--|
| For size | B1 | B2 | D1 Ø | D2 | H1 +12/-2 | H2 | Н3 | H4 | H5 | Н6 | H7 | | |
| 30 | 58 | 3 | 33 | M8 | 58 | 22 | 11.5 | 4 | 19.5 | 13.5 | 11 | | |

| For size | L1 | W1 | W2 | = ©1 | = ©2 | Weight [g] | Part no. | Туре |
|----------|----|-----|----|-------------|-------------|---------------|----------|-------------|
| 30 | 40 | 12° | 6° | 17 | 13 | 160 | 4706964 | EADC-E11-30 |


Mounting kit EAHT-E9


For size 30

Material: Anodised aluminium RoHS-compliant

Prepared hole patterns for:

- Mini slide EGSL-35
- Mini slide DGSL-8/-10/-12
- Electric slide EGSK-20/-26
- Electric cylinder EPCO-16
- Mini slide EGSC-BS-25/-32





| Dimensions and | d ordering data | | | | | | | | | | | |
|----------------|-----------------|-----|-----|-----|---------------|------------|---------------|------|----------------|---------------|---------------|---------|
| For size | B1 | B2 | В3 | B4 | B5 | В6 | В7 | B8 | B9 | B10 | D1 Ø H7 | D2 Ø |
| 30 | 50 | 40 | 36 | 25 | 24 | 42 | 35 | 20 | 18 | 26 | 5 | 4.5 |
| For size | D3 | D4 | D5 | D6 | D7 Ø H7 | D8 | D9 Ø H7 | D10 | D11 Ø H7 | D12 Ø | D13 Ø | D14 |
| 30 | M4 | M5 | M4 | M4 | 7 | M5 | 7 | M4 | 7 | 4.5 | 4.5 | M4 |
| For size | D15 | D16 | D17 | H1 | H2 | Н3 | H4 ±0.2 | H5 | H6 | H7 | Н8 | Н9 |
| 30 | M3 | M4 | M4 | 125 | 85 | 40 | 118 | 90 | 80 | 15 | 50 | 30 |
| For size | H10 | H11 | H12 | H13 | H14 | H15 | H16 | H17 | H18 | H19 | L1 | L2 |
| 30 | 40 | 20 | 20 | 55 | 60 | 9 | 40 | 20.5 | 40 | 10.5 | 65 | 42 |
| For size | L3 | L4 | L5 | L6 | T1 ±0.1 | T2 ±0.1 | Weight [g] | | Part no. | Туре | | |
| 30 | 15 | 20 | 6 | 5 | 1.6 | 1.6 | 165 | | 4070088 | EAHT-E9-FB-3D |)-30 | |

Sensor mounting EAPR

For size 30 (incl. switch lug)


Material:

Retaining bracket: Wrought aluminium

alloy

Switch lug: steel





| Dimensions and ord | Dimensions and ordering data | | | | | | | | | | | | | |
|--------------------|------------------------------|----|----|----|-----|-----|-----|-----|-----|-----|--|--|--|--|
| For size | B1 | B2 | В3 | B4 | B5 | B6 | D1 | D2 | D3 | H1 | | | | |
| | | | | | | | Ø | Ø | Ø | | | | | |
| 30 | 51.5 | 5 | 39 | 23 | 8.4 | 5.3 | 6.5 | 3.4 | 2.6 | 40 | | | | |
| | l | 1 | l | 1 | l | l | 1 | 1 | 1 | 1 | | | | |
| For size | H2 | H3 | H4 | H5 | H6 | H7 | L1 | L2 | L3 | L4 | | | | |
| 20 | 20 | 22 | 12 | 8 | (| 2 | 20 | 22 | 0 | 1.5 | | | | |
| 30 | 28 | 23 | 13 | 8 | 6 | 3 | 30 | 22 | 8 | 15 | | | | |

| For size | L5 | L6 | L7 | L8 | T1 | Weight [g] | Part no. | Туре |
|----------|-----|-----|----|-----|----|---------------|----------|-------------|
| 30 | 4.5 | 6.5 | 3 | 2.5 | 2 | 330 | 2319236 | EAPR-E11-30 |

Energy chain and connection set for size 30 Ordering data – Energy chain EADH-U-30-30 EAD







| Туре | | D1 Ø | H1 | H2 |
|------|--------------|---------|------|----|
| | EADH-U-3D-30 | 34.5 | 12.5 | 11 |
| | EADH-U-3D-40 | 45 | 15 | - |

| For size | Max. bending radius [mm] | Length [mm] | Weight [g] | Part no. | Туре |
|----------|-----------------------------|-------------|---------------|----------|--------------|
| 30 | 50 | Approx. 500 | 75 | 8059999 | EADH-U-3D-30 |
| | 58 | Approx. 500 | 100 | 8060324 | EADH-U-3D-40 |


| Ordering data – Connection set | | | | |
|--------------------------------|------------------------------|-------------|--------------------|---------------|
| | For energy chain | Description | Part no. | Туре |
| 8888 | EADH-U-3D-30 EADH-U-3D-40 | 3 37 | 8060325 8060326 | EAHT-AE-3D-40 |
| | | | | |


Adjusting kit EADC-E12

For size 40

Material: Anodised aluminium RoHS-compliant

For mounting and aligning the planar surface gantry. The kit is height adjustable.





| Dimensions and ordering data | | | | | | | | | | | | |
|------------------------------|-----|----|----|------|----|----|----|-------|--|--|--|--|
| For size | B1 | B2 | В3 | B4 | B5 | D1 | H1 | H2 | | | | |
| | | | | ±0.2 | | | | | | | | |
| 40 | 110 | 78 | 26 | 36.5 | 5 | M8 | 29 | 129.8 | | | | |

| For size | H3 min. max. | | H4 L1 | | T1 | T1 Weight | | Туре |
|----------|-------------------|------|-------|----|------|-----------|---------|-------------|
| | min. | max. | max. | | ±0.1 | [g] | | |
| 40 | 34.8 | 39.8 | 14 | 37 | 10 | 800 | 8029165 | EADC-E12-40 |


Mounting kit EAHM-E12

For size 40

Material: Anodised aluminium RoHS-compliant

For mounting the planar surface gantry. The kit is not height adjustable.





[2] Width of elongated hole The mounting kit cannot be used for compensation.

| Dimensions and ordering data | | | | | | | | | | | | |
|------------------------------|-----|----|----|------|----|----|------|--|--|--|--|--|
| For size | B1 | B2 | В3 | B4 | B5 | D1 | H1 | | | | | |
| | | | | ±0.2 | | | ±0.2 | | | | | |
| 40 | 110 | 78 | 26 | 36.5 | 5 | M8 | 30 | | | | | |

| For size | H2 | H4 max. | L1 | T1 ±0.1 | Weight [g] | Part no. | Туре |
|----------|-------|------------|----|------------|------------|----------|---------------|
| 40 | 131.3 | 14 | 37 | 10 | 330 | 3489340 | EAHM-E12-K-40 |

Sensor mounting EAPR

For size 40

Material:


Switch lug: steel


Sensor bracket: wrought aluminium

alloy

RoHS-compliant

For proximity switches SIES-V3B and SIES-Q8B (for sensing the position of the slide on the X-axis)





| Dimensions and orde | ering data | | | | | | | | | |
|---------------------|------------|------|----|------|----|------|-----|-----|------|------|
| For size | B1 | B2 | В3 | H1 | H2 | Н3 | H4 | H5 | Н6 | H7 |
| | | | | | | ±0.1 | | | -0.1 | -0.2 |
| 40 | 44 | 36.3 | 4 | 21.8 | 21 | 15 | 2.5 | 6.1 | 3.1 | 3 |

| For size | L1 | L2 | L3 | L4 | Weight [g] | Part no. | Туре |
|----------|----|----|----|----|---------------|----------|-------------|
| 40 | 36 | 20 | 35 | 25 | 120 | 2536353 | EAPR-E12-40 |


H-rail mounting CAFM

For H-rail to EN 50022

Material:

Anodised aluminium

RoHS-compliant



| Dimensions and | ordering data | | | | | | | |
|----------------|---------------|------|----|----|----|--------|----------|-----------|
| D1 | H1 | H2 | L1 | L2 | L3 | Weight | Part no. | Туре |
| Ø | | | | | | [g] | | |
| 4.2 | 52 | 22.5 | 50 | 34 | 8 | 29 | 4135048 | CAFM-D3-H |

| Proximity switc Ordering data - | hes for size 30 · Proximity switches for T-slot, inductive | | | | | Data sheets → Internet: sies |
|------------------------------------|---|-----------------------|------------------|------------------|----------|------------------------------|
| | Type of mounting | Electrical connection | Switching output | Cable length [m] | Part no. | Туре |
| N/O contact | | | | | | |
| | Inserted in the slot from above, flush with | Cable, 3-wire | PNP | 7.5 | 551386 | SIES-8M-PS-24V-K-7.5-0E |
| S | the cylinder profile | Plug M8x1, 3-pin | | 0.3 | 551387 | SIES-8M-PS-24V-K-0.3-M8D |
| | | Cable, 3-wire | NPN | 7.5 | 551396 | SIES-8M-NS-24V-K-7.5-0E |
| | | Plug M8x1, 3-pin | | 0.3 | 551397 | SIES-8M-NS-24V-K-0.3-M8D |
| N/C contact | | | , | | | |
| | Inserted in the slot from above, flush with | Cable, 3-wire | PNP | 7.5 | 551391 | SIES-8M-PO-24V-K-7.5-0E |
| S | the cylinder profile | Plug M8x1, 3-pin | | 0.3 | 551392 | SIES-8M-PO-24V-K-0.3-M8D |
| | | Cable, 3-wire | NPN | 7.5 | 551401 | SIES-8M-NO-24V-K-7.5-OE |
| _ | | Plug M8x1, 3-pin | | 0.3 | 551402 | SIES-8M-NO-24V-K-0.3-M8D |



For homing in combination with third-party motors.

Inserted in the slot from above, flush with

the cylinder profile

| , | ritches for size 40 proximity switch for sensing the position of the | e slide on the Y-axis | | | | |
|---------------|--|-----------------------|---------------------|------------------|----------|------------------------------|
| Ordering dat | a – Proximity switches for T-slot, inductive | | | | | Data sheets → Internet: sies |
| | Type of mounting | Electrical connection | Switching output | Cable length [m] | Part no. | Туре |
| | Inserted in the slot from above, flush with the cylinder profile | Plug M8x1, 3-pin | PNP, N/O contact | 0.3 | 551387 | SIES-8M-PS-24V-K-0.3-M8D |
| ' | proximity switches for sensing the positions or a — Proximity switches for T-slot | the Z-axis | | | | Data sheets → Internet: smt |
| | Type of mounting | Electrical connection | Switching output | Cable length [m] | Part no. | Туре |
| With mini sli | ide DGSL (magneto-resistive) | | | | | |
| 2.30 | Inserted in the slot from above, flush with the cylinder profile | Plug M8x1, 3-pin | PNP, N/O contact | 0.3 | 551367 | SME-10M-DS-24V-E-0.3-L-M8D |
| With mini sli | ide EGSL (inductive) | | | | | |
| | | D1 110 1 0 1 | DILLE | | | |

PNP,

N/O contact

Plug M8x1, 3-pin

0.3

551387

SIES-8M-PS-24V-K-0.3-M8D

| Ordering data – Proxin | nity switches | | | | | Data sheets → Internet: |
|---|-------------------------------|-----------------------|-------|---------------------|----------|---|
| | Type of mounting | Electrical connection | Switc | hing output | Part no. | Туре |
| N/O contact | | | | | | |
| | Screwed on | Plug M8x1, 3-pin | PNP | | 150491 | SIES-V3B-PS-S-L |
| N/C contact | | | | | | |
| 5.35 | Screwed on | Cable, 3-wire | NPN | | 174550 | SIES-Q8B-NO-K-L |
| Ordering data | | <u> </u> | | | | |
| | Description | | | Cable length [m] | Part no. | Туре |
| Control cable NEBC | | | | | | |
| | For the I/O interface to any | controller | | 1 | 2307459 | NEBC-S1H15-E-1.0-N-LE15 |
| | | | | 2.5 | 2052917 | NEBC-S1H15-E-2.5-N-LE15 |
| | | | | 5 | 2052918 | NEBC-S1H15-E-5.0-N-LE15 NEBC-S1H15-E-10.0-N-LE15 |
| - | | | | 10 | 2052919 | NEDC-S1R15-E-10.0-N-LE15 |
| Cables for Z-axis for si Ordering data | ze 40 | | | | | |
| Ordering data | Description | | | Cable length | Part no. | Туре |
| Motor cable NEBM | | | | | | |
| | Min. bending radius: 62 m | | | 10 | 1450372 | NEBM-S1G9-E-10-Q5-LE6 |
| | Suitable for energy chains | | | | | |
| | • Ambient temp.: -40 +80°C | | | | | |
| Encoder cable NEBM | | | | | | |
| | Min. bending radius: 51 m | ım | | 10 | 550749 | NEBM-M12G8-E-10-S1G9 |
| | Suitable for energy chains | | | 15 | 550750 | NEBM-M12G8-E-15-S1G9 |
| | Ambient temp.: 7006 | | | | | |
| | −40 +70°C | | | | | |