
Cylinders with holding brake DFLC/G





Cylinders with holding brake DFLC/G

Characteristics

At a glance

Holding brakes are generally used to dynamically brake a movement or to prevent round rods of different lengths from starting up at any position. The double-acting cylinders with holding brake DFLC/G can brake or clamp the piston rod. During clamping, the piston rod is securely locked so that the application of external force does not produce any relative motion. A rod can be locked at any position along the stroke, whether in the end positions or the intermediate positions. This provides protection in the event of a pressure failure and secures the piston rod during intermediate stops for process operations.

- The clamping force is released when compressed air is supplied to the holding brake
- Static holding force up to 17000 N
- The cylinders with holding brake are based on ISO 15552 (previously

also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)

NEW

- 🏺 - Note

The cylinders with holding brake DFLC/G-...-S are a safety device as defined in the Machinery Directive 2006/42/EC and have been tested and certified to relevant standards. Additional information is available at www.festo.com/sp \rightarrow Certificates. The cylinders with holding brake DFLC/G-...-EX4-S are suitable for use in ATEX zones in "static holding" mode.

Possible safety functions:

- · Holding function: retaining the piston rod by clamping with frictional locking
- Emergency braking function: stopping the movement of the piston rod by clamping with frictional locking

The safety functions are triggered by switching off the compressed air supply or by the failure of the compressed air supply.

Cushioning

[PPV] Pneumatic cushioning adjustable at both ends



- The drive is fitted with pneumatic end-position cushioning, which can be adapted by the operator for maximum performance according to the moved mass and speed.
- Very powerful

Corrosion protection

[R3] High corrosion protection




· Protects the drive against corrosion

Certification

[S] Safety device

• To Machinery Directive 2006/42/EC

Position sensing





• For monitoring the switching status of the holding brake

[EX4] II 2GD


- ATEX category for gas II 2G
- ATEX category for dust II 2D
- Type of ignition protection for gas $\operatorname{Ex}\nolimits h$ IIC T4 Gb
- Type of ignition protection for dust Ex h IIIC T120°C Db
- Explosion-proof ambient temperature $-20 \le Ta \le +60$

2

Type codes

001	Series	005	Position sensing
DFLC	Cylinder with holding brake	A	For proximity sensor
002	Piston diameter	006	Corrosion protection
40	40		Standard
63	63	R3	High corrosion protection
100	100	007	EU certification
003	Stroke		None
	10 2000	EX4	II 2GD
004	Cushioning	008	Certification
PPV	Pneumatic cushioning, adjustable at both ends	S	Safety component to Machinery Directive 2006/42/EC

Peripherals overview



Peripherals overview

	Type/order code	Description	→ Page/Internet
[1]	Foot mounting	For bearing or end caps	22
	HNC/CRHNC		
[2]	Flange mounting	For bearing or end caps	23
	FNC/CRFNG	 Suitable for emergency stop applications/dynamic braking 	
[3]	Swivel flange	For end caps	25
	SNC		
4]	Clevis foot	Weld-on, with spherical bearing	31
	LSNG		
5]	Swivel flange	With spherical bearing for end caps	26
	SNCS/SNCSR3		
6]	Clevis foot	-	31
	LBG/LBGR3		
7]	Swivel flange	For end caps	27
	SNCL		
8]	Swivel flange	For end caps	28
	SNCB/SNCBR3		
9]	Clevis foot	-	31
	LNG/CRLNG		
10]	Clevis foot	With spherical bearing	31
	LSN		
11]	Rod eye	With spherical bearing	32
	SGS/CRSGS		
12]	Rod clevis	With male thread	32
	SGA		
13]	Coupling piece	For compensating radial deviations	32
	KSG		
14]	Rod clevis	Permits a swivelling movement of the cylinder in one plane	32
	SG/CRSG		
15]	Self-aligning rod coupler	For compensating radial and angular deviations	32
	FK, CRFK		
16]	Push-in fitting	For connecting compressed air tubing with standard O.D.	qs
	QS		
17]	One-way flow control valve	For speed regulation	35
	GRLA		
18]	Sensor kit	 Inductive sensor kit for status sensing of the clamping function 	33
	DADG	Not included in scope of delivery	
19]	Proximity switch	For sensing the piston position	34
	SMT-8M-A	Not included in scope of delivery	
20]	Position transmitter	Continuously senses the position of the piston	35
	SDAT-MHS	Has an analogue output	
		Not included in scope of delivery	

- 📲 - Note

Only flange mounting FNC/CRFNG is permissible for emergency stop applications/dynamic braking. Additional accessories for this application are available on request.

Cylinders with holding brake DFLC

NEW

Data sheet







- Stroke length
- 10 ... 2000 mm



General technical data

General technical data						
Piston diameter		40	63	100		
Design		Piston				
		Piston rod				
		Profile barrel				
Variants		Piston rod at one end				
Mode of operation		Double-acting				
Pneumatic connection		I				
Cylinder		G1/4	G3/8	G1/2		
Holding brake		G1/8	G1/8	G3/8		
Piston rod thread		M12x1.25	M16x1.5	M20x1.5		
Piston rod end		Male thread	L			
Cushioning		Pneumatic cushioning adjus	table at both ends			
Cushioning length	[mm]	19	22	31		
Position sensing		Via proximity switch	l	·		
Type of mounting		Via female thread				
		With accessories				
Type of clamping with active direction		At both ends				
		Clamping via spring force, re	leased via compressed air			
Mounting position		Any				
Operating and environmental condit	ions					
Piston diameter		40	63	100		
Cylinder		I.				
Operating pressure	[bar]	0.6 8				
Holding brake						
Min. release pressure	[bar]	3.8				
Max. permissible test pressure						
	[bar]	8				
Operating medium	[bar]		-1:2010 [7:4:4]			
Operating medium Note on operating/	[bar]	Compressed air to ISO 8573 Operation with lubricated me				
	[bar]	Compressed air to ISO 8573				
Note on operating/	[bar] [°C]	Compressed air to ISO 8573		-10+80		
Note on operating/ pilot medium		Compressed air to ISO 8573 Operation with lubricated me		-10+80		
Note on operating/ pilot medium Ambient temperature ¹⁾		Compressed air to ISO 8573 Operation with lubricated me		-10+80		

1) Note operating range of proximity switches.

2) Corrosion resistance class CRC 1 to Festo standard FN 940070

Low corrosion stress. Dry internal application or transport and storage protection. Also applies to parts behind coverings, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions). Corrosion resistance class CRC 3 to Festo standard FN 940070

High corrosion stress. Outdoor exposure under moderate corrosive conditions. Externally visible parts with primarily functional surface requirements which are in direct contact with a normal industrial environment.

Data sheet

Safety characteristics

Salety thatacteristics				
Piston diameter	40	63	100	
Conforms to standard	This product is based on ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)			
Safety function	Holding and stopping a movement			
Performance Level (PL)	Stopping, holding, blocking a movement/category 1, Performance Level c			
Certification	German Technical Control Board (TÜV)			
Certificate issuing authority German Technical Control Board (TÜV) CA 697				
CE marking ¹⁾ (see declaration of conformity)	To EU Machinery Directive			

1) For information about the area of use, see the EC declaration of conformity at: www.festo.com/sp → Certificates.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

ATEX				
Piston diameter	40	63	100	
ATEX category for gas	II 2G			
Type of ignition protection for gas	Ex h IIC T4 Gb			
ATEX category for dust	II 2D			
Type of ignition protection for dust	Ex h IIIC T120°C Db			
Explosion-proof ambient temperature [°C]	-20 ≤ Ta ≤ +60			
	-20 ≤ Ta ≤ +60			
Explosion-proof ambient temperature [°C] Weight [g] Piston diameter	-20 ≤ Ta ≤ +60	63	100	
Weight [g]		63 6185	100	
Weight [g] Piston diameter	40			
Weight [g] Piston diameter Basic weight with 0 mm stroke	40 2930	6185	19120	

Forces [N]

Piston diameter	40	63	100
Theoretical force at 6 bar, advancing	754	1870	4712
Theoretical force at 6 bar, retracting	633	1682	4418
Static holding force	1350	3300	8200

25

--Note

The specified holding force refers to a static load. If this value is exceeded, slippage may occur. Dynamic forces occurring during operation must

Additional moving mass per 10 mm stroke

not exceed the static holding force if slippage Lateral loads and bending moments on the is to be avoided. The holding brake is backlash-free in the clamped condition when varying loads are applied to the piston rod.

16

piston rod can impair the function. (Make sure that the load on the piston rod is only in the direction of movement.)


Actuation:

40


The holding brake may only be released when the forces on the piston rod have reached equilibrium. Otherwise there is a risk of accidents due to the sudden movement of the piston rod. Blocking off the compressed air supply at both ends (e.g. with a 5/3-way valve) does not provide any safety.

Data sheet

Load mass m as a function of piston speed $v_{\rm 0}$




Stopping distance sk_0 as a function of piston speed \textbf{v}_0 ø 40



All data in the graphs is intended exclusively for the purposes of preselection when configuring the emergency braking function and must be checked mathematically and in practice prior to commissioning. Additional information is available at www.festo.com/sp \rightarrow User documentation.

NEW

Data sheet




Cylinder with holding brake

[1]	Piston rod	Hard-chrome-plated steel
[2]	Cover	Die-cast aluminium
		Wrought aluminium alloy
[3]	Housing	Steel
[4]	Cylinder barrel	Smooth-anodised wrought aluminium alloy
-	Seals	NBR
		TPE-U(PU)
-	Note on materials	RoHS-compliant

Cylinders with holding brake DFLC

NEW

Data sheet



[5] Connection to release clamping function

NEW

Data sheet

ø	A	В	BG	BG1	BG2	E	E1	E2	E3	EE
		Ø	min.							
[mm]	-0.5	d11				±0.8	+0.5	±1		
40	24	35	16	8	13.2	54	54	74.1	15	G1/4
63	32	45	16	9	14.8	78	75	98.1	15	G3/8
100	40	55	17	10	14.8	124	110	152.1	22	G1/2
Ø	EE1	G	G1	G2	J1	J2	КК	L2	L3	L4
[mm]								±1		
40	G1/8	33	27	40	4	8	M12x1.25	186	29	116
63	G1/8	40.5	30	44	6.25	12.75	M16x1.5	210	38.4	122.5
100	G3/8	48	35	54	10	13.5	M20x1.5	255	47.1	148.5
ø	L5	L6	L8+	L9	MM	PL	PL1	PL2	R1	RN
					ø					
[mm]			±0.4							
40	6.5	5.5	105	49.4	16	22.5	7.5	9.6	R8	98
63	6.5	6	121	53.6	20	27.5	9	9.6	R10	100
100	8	-	138	65.3	25	31.5	7.5	13.6	R15	120
Ø	RT	TG	VA	VD	W1	WH	ZJ+	=©1	= ©2	=©3
[mm]		±0.3	-0.2	±0.2		+3.2/-1	+2.6/-0.4			
40	M6	38	4	5	27°	28.7	319.7	13	19	6
63	M8	56.5	4	5	20°	35.9	366.9	17	24	8
100	M10	89	4	5	20°	49.3	442.3	22	30	6

Ordering data – Modular product system


Ordering table							
Size		40	63	100	Conditions	Code	Enter code
Module no.		8073331	8073332	8073333			
Function		Cylinder with holding br	ake, double-acting			DFLC	DFLC
Piston diameter	[mm]	40	63	100			
Stroke	[mm]	10 2000					
Cushioning		Pneumatic cushioning, a	adjustable at both ends			-PPV	-PPV
Position sensing		Via proximity switch				Α	A
Corrosion protection		Standard					
		High corrosion protectio	n			-R3	
EU certification		None					
		II 2GD				-EX4	
Certification		Safety device to Machine	ery Directive 2006/42/EC			-S	-S

Type codes

001	Series	
DFLG	Cylinder with holding brake	
002	Piston diameter	
160	160	
003	Stroke	
	10 2000	
004	Cushioning	
PPV	Pneumatic cushioning, adjustable at both ends	

005	Position sensing
Α	For proximity sensor
006	Corrosion protection
	Standard
R3	High corrosion protection
007	EU certification
	None
EX4	II 2GD
008	Certification
S	Safety component to Machinery Directive 2006/42/EC

Peripherals overview



Peripherals overview

Accessories

	Type/order code	Description	→ Page/Internet
[1]	Foot mounting	For bearing and end caps, corresponds to MS1 to ISO 15552	22
	HNG		
2]	Flange mounting	For bearing or end caps, corresponds to MF1/MF2 to ISO 15552	24
	FNG	Suitable for emergency stop applications/dynamic braking	
3]	Swivel flange	For end caps	29
	SNG		
4]	Clevis foot	With spherical bearing	31
	LSNG		
5]	Swivel flange	For end caps, corresponds to MP2 to ISO 15552	29
	SNGL		
6]	Swivel flange	For end caps, corresponds to MP2 to ISO 15552	30
	SNGB		
7]	Clevis foot	For swivel flange SNGB	31
	LN		
8]	Clevis foot	With spherical bearing	31
	LSN		
[9]	Rod eye	With spherical bearing	32
-	SGS		
10]	Rod clevis	Suitable for spherical mounting of cylinders in conjunction with rod eye SGS	32
	SGA		
[11]	Rod clevis	Permits a swivelling movement of the cylinder in one plane	32
	SG		
12]	Self-aligning rod coupler	For compensating radial and angular deviations	32
-	FK		
13]	Push-in fitting	For connecting compressed air tubing with standard O.D.	qs
- 1	QS		1-
14]	One-way flow control valve	For speed regulation	35
	GRLA		
15]	Sensor kit	Inductive sensor kit for status sensing of the clamping function	33
	DADG	Not included in scope of delivery	
16]	Sensor mounting	For proximity switch SME-8M-A and position transmitter SDAT-MHS	35
	DASP		
[17]	Proximity switch	For sensing the piston position	34
	SMT-8M-A	Can be integrated in the cylinder profile barrel	
		 Not included in scope of delivery 	
18]	Position transmitter	Continuously senses the position of the piston	35
- •1	SDAT-MHS	Has an analogue output	
		Can be integrated in the cylinder profile barrel	
		 2 sensor mountings DASP are required for mounting 	
		Not included in scope of delivery	

- 🎍 - Note

Only flange mounting FNG is permissible for emergency stop applications/dynamic braking. Additional accessories for this application are available on request.

Cylinders with holding brake DFLG

NEW

Data sheet

Function



- Ø Diameter 160 mm
 - Stroke length 10 ... 2000 mm



General technical data

Piston diameter	160
Design	Piston
	Piston rod
	Profile barrel
Variants	Piston rod at one end
Mode of operation	Double-acting
Pneumatic connection	
Cylinder	63/4
Holding brake	G3/8
Piston rod thread	M36x2
Piston rod end	Male thread
Cushioning	Pneumatic cushioning adjustable at both ends
Cushioning length [mm]	48
Position sensing	Via proximity switch
Type of mounting	Via female thread
	With accessories
Type of clamping with active direction	At both ends
	Clamping via spring force, released via compressed air
Mounting position	Any

Operating and environmental conditions

Operating and environmental condit	10115					
Piston diameter		160				
Cylinder						
Operating pressure	[bar]	0.6 8				
Holding brake						
Min. release pressure	[bar]	3.8				
Max. permissible test pressure	[bar]	8				
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]				
Note on operating/		Operation with lubricated medium not possible				
pilot medium						
Ambient temperature ¹⁾	[°C]	-20 +80				
Corrosion resistance class CRC ²⁾						
[] Standard		1				
[R3] High corrosion protection		3				

1) Note operating range of proximity switches.

2) Corrosion resistance class CRC 1 to Festo standard FN 940070

Low corrosion stress. Dry internal application or transport and storage protection. Also applies to parts behind coverings, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions). Corrosion resistance class CRC 3 to Festo standard FN 940070

High corrosion stress. Outdoor exposure under moderate corrosive conditions. Externally visible parts with primarily functional surface requirements which are in direct contact with a normal industrial environment.

I

Data sheet

Safety characteristics

Surety characteristics	
Piston diameter	160
Conforms to standard	This product is based on ISO 15552 (previously also VDMA 24562, ISO 6431, NF E49 003.1, UNI 10290)
Safety function	Holding and stopping a movement
Performance Level (PL)	Stopping, holding, blocking a movement/category 1, Performance Level c
Certification	German Technical Control Board (TÜV)
Certificate issuing authority	German Technical Control Board (TÜV) CA 697
CE marking ¹⁾ (see declaration of conformity)	To EU Machinery Directive

1) For information about the area of use, see the EC declaration of conformity at: www.festo.com/sp → Certificates.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

ATEX	
Piston diameter	160
ATEX category for gas	II 2G
Type of ignition protection for gas	Ex h IIC T4 Gb
ATEX category for dust	II 2D
Type of ignition protection for dust	Ex h IIIC T120°C Db
Explosion-proof ambient temperature [°C]	$-20 \le Ta \le +60$

Weight [g]	
Piston diameter	160
Basic weight with 0 mm stroke	49660
Additional weight per 10 mm stroke	208
Moving mass with 0 mm stroke	7085
Additional moving mass per 10 mm stroke	97
Forces [N]	
Piston diameter	160
Theoretical force at 6 bar, advancing	12064
Theoretical force at 6 bar, retracting	11310

--Note

Static holding force

The specified holding force refers to a static load. If this value is exceeded, slippage may occur. Dynamic forces occurring during operation must

not exceed the static holding force if slippage Lateral loads and bending moments on the is to be avoided. The holding brake is backlash-free in the clamped condition when varying loads are applied to the piston rod.

17000


piston rod can impair the function. (Make sure that the load on the piston rod is only in the direction of movement.)

Actuation:

The holding brake may only be released when the forces on the piston rod have reached equilibrium. Otherwise there is a risk of accidents due to the sudden movement of the piston rod. Blocking off the compressed air supply at both ends (e.g. with a 5/3-way valve) does not provide any safety.


Data sheet

Load mass m as a function of piston speed \boldsymbol{v}_0



..... DFLG-160

Stopping distance sk_0 as a function of piston speed v_0




- 📲 - Note

All data in the graphs is intended exclusively for the purposes of preselection when configuring the emergency braking function and must be checked mathematically and in practice prior to commissioning. Additional information is available at www.festo.com/sp \rightarrow User documentation.

NEW

NEW

Data sheet




Cylinder with holding brake

	-							
[1]	Piston rod	Hard-chrome-plated steel						
[2]	Cover	Die-cast aluminium						
		Wrought aluminium alloy						
[3]	Housing	Steel						
[4]	Cylinder barrel	Smooth-anodised wrought aluminium alloy						
-	Seals	NBR						
		TPE-U(PU)						
-	Note on materials	RoHS-compliant						

Cylinders with holding brake DFLG

Data sheet



+ = plus stroke length

* = installation space for sensor kit DADG-D-F8

[1] Socket head screw with female thread for mounting components

[2] Adjusting screw for adjustable end-position cushioning

[3] Position for proximity switch (thread M6x0.75)

[4] Sensor kit DADG-D-F8

[5] Connection to release clamping function

BG1 В BG BG2 Е E1 E2 E3 EE А Ø min. Ø [mm] -0.5 d11 ±0.8 ±0.9 ±1 160 72 65 24 14 21 195 186 222.6 22 G3/4 Ø EE1 G G1 G2 J1 J2 KK L1 L2 L3 [mm] ±1 G3/8 M36x2 298 160 50.7 48 80 12 20 12 67.2 L4 L5 L8+ L9 MM PL PL1 PL2 R RN Ø Ø [mm] ±1 160 143.5 8 180 95.5 40 31 5 13.1 R30 155 RT TG VA VD W1 WH ZJ+ **=**@1 **=**©2 **=**©3 Ø [mm] ±1.1 -1 ±0.2 +2.3/-2.3 +2.3/-2.3 160 M16 140 6 7 20° 558 36 55 24 80

NEW


Ordering data – Modular product system

Ordering table					
Size		160	Conditions	Code	Enter code
Module no.		8073334			
Function		Cylinder with holding brake, double-acting		DFLG	DFLG
Piston diameter	[mm]	160		-160	-160
Stroke	[mm]	10 2000			
Cushioning		Pneumatic cushioning, adjustable at both ends		-PPV	-PPV
Position sensing		Via proximity switch		A	A
Corrosion protection		Standard			
		High corrosion protection		-R3	
EU certification		None			
		II 2GD		-EX4	
Certification		Safety device to Machinery Directive 2006/42/EC		-S	-S


Accessories

Foot mounting HNC/CRHNC for DFLC





Material:



Dimensions and ordering data

For diam.	AB Ø	AH	AO	AT	AU	E	SA	TR	ХА	XS
[mm]										
40	10	36	9	4	28	54	347	36	347.7	56.7
40 63	10 10	36 50	9 12.5	4	28 32	54 75	347 395	36 50	347.7 398.9	56.7 67.9

For diam.	Basic type				Corrosion-resistant				
	CRC ¹⁾	Weight	Part no.	Type ²⁾	CRC ¹⁾	Weight	Part no.	Type ²⁾	
[mm]		[g]				[g]			
40	2	193	174370	HNC-40	4	188	176938	CRHNC-40	
63	2	436	174372	HNC-63	4	424	176940	CRHNC-63	
100	2	1009	174374	HNC-100	4	990	176942	CRHNC-100	

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment. Corrosion resistance class CRC 4 to Festo standard FN 940070

Particularly high corrosion stress. Outdoor exposure under extreme corrosive conditions. Parts exposed to aggressive media, e.g. in the chemical or food industries. Such applications may need to be safeguarded by special tests (\rightarrow also FN 940082), using appropriate media.

2) Suitable for ATEX


Foot mounting HNG

for DFLG

Material:

Galvanised steel Free of copper and PTFE





Dimensions and ordering data

DIIIICIISIOIIS	and order	ilig uata												
For diam.	AB	AH	AO	AT	AU	E	SA	TR	XA	XS	CRC ¹⁾	Weight	Part no.	Type ²⁾
	ø													
[mm]												[g]		
160	18.5	115	20	10	60	169	598	115	618	140	2	3931	34476	HNG-160

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

2) Suitable for ATEX

NEW


Accessories

Flange mounting FNC/CRFNG for DFLC

Suitable for emergency stop applications/ dynamic braking



Material: FNC: galvanised steel CRFNG: high-alloy steel Free of copper and PTFE RoHS-compliant



+ = plus stroke length

Dimensions and ordering data

Dimensions and	i oracim5 aata							
For diam.	E	FB	MF	R	TF	UF	W	ZF
		ø						
[mm]		H13						
40	54	9	10	36	72	90	18.7	329.7
63	75	9	12	50	100	120	23.9	378.9
100	110	14	16	75	150	175	33.3	458.3

For diam.	Basic type				Corrosion-re	sistant		
	CRC ¹⁾	Weight	Part no.	Type ²⁾	CRC ¹⁾	Weight	Part no.	Type ²⁾
[mm]		[g]				[g]		
40	1	291	174377	FNC-40	4	291	161847	CRFNG-40
63	1	679	174379	FNC-63	4	680	161849	CRFNG-63
05	-	0, 1	-1.515					

1) Corrosion resistance class CRC 1 to Festo standard FN 940070

Low corrosion stress. Dry internal application or transport and storage protection. Also applies to parts behind coverings, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions). Corrosion resistance class CRC 4 to Festo standard FN 940070

Particularly high corrosion stress. Outdoor exposure under extreme corrosive conditions. Parts exposed to aggressive media, e.g. in the chemical or food industries. Such applications may need to be safeguarded by special tests (\rightarrow also FN 940082), using appropriate media.

2) Suitable for ATEX


Cylinders with holding brake DFLC/G

NEW


Accessories

Flange mounting FNG for DFLG

Suitable for emergency stop applications/ dynamic braking



Material: Painted spheroidal graphite cast iron Free of copper and PTFE RoHS-compliant



Dimensions and ordering data

Dimension	s and ordering	guala										
For diam.	E	FB	MF	R	TF	UF	W	ZF	CRC ¹⁾	Weight	Part no.	Type ²⁾
		ø										
[mm]		H13								[g]		
160	180	18	20	115	230	280	60	578	1	3550	34478	FNG-160

1) Corrosion resistance class CRC 1 to Festo standard FN 940070

Low corrosion stress. Dry internal application or transport and storage protection. Also applies to parts behind coverings, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions). Suitable for ATEX

NEW


Accessories

Swivel flange SNC for DFLC



Material:

Die-cast aluminium



Dimensions and ordering data

For diam.	CF Ø	CG	СР	E	FM		L	SR
[mm]	E7/h9	H14	h14		±0.2			
40	12	16	40	54 _{-0.5}	25		16	12
63	16	21	51	75 _{-0.6}	32		21	16
100	20	25	75	110+0.3/-0.8	41		27	20
For diam.	-	ſĠ		ХС	CRC ¹⁾	Weight	Part no.	Type ²⁾
[mm]						[g]		
40		38		344.7	1	140	174384	SNC-40
63	5	6.5		398.9	1	331	174386	SNC-63
100	8	39		483.3	1	865	174388	SNC-100

1) Corrosion resistance class CRC 1 to Festo standard FN 940070


Low corrosion stress. Dry internal application or transport and storage protection. Also applies to parts behind coverings, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions). 2) Suitable for ATEX

Cylinders with holding brake DFLC/G

Accessories

Swivel flange SNCS/SNCS-...-R3 for DFLC





+ = plus stroke length

Material:

SNCS 63 ... 100: Wrought aluminium alloy SNCS-...-R3 100:

SNCS 40: die-cast aluminium

Dimensions and ordering data

For diam.		CX		DL		E		EP
		[CRSNCS]	[SNCSR3]			[CRSNCS]	[SNCSR3]	
[mm]				±0.2				±0.2
40	12+0.015	12+0.018/-0.04	-	25	54 _{-0.5}	54 _{-0.5}	-	12
40 63	12 _{+0.015} 16 _{+0.015}	12 _{+0.018/-0.04} 16 _{+0.018/-0.14}	-	25 32	54 _{-0.5} 74.5 _{±0.5}	54 _{-0.5} 75 _{-0.6}		12 15

Dimensions and ordering data

For diam.	EX	LT		MS		R	A		TG	XC
				[CRSNCS]	[SNCSR3]		[CRSNCS]	[SNCSR3]		
[mm]						+1	+1	+1		
40	16	16	17 _{+0.5}	17 _{+0.5}	-	17.5	17.5	-	38	344.7
63	21	21	23 _{-0.5}	22 _{+0.5}	-	23	23	-	56.5	398.9
100	25	27	30 _{±0.5}	-	30 _{±0.5}	95	-	100	89	483.3

For diam.	Basic type				High corrosion	n protection		
	CRC ¹⁾	Weight	Part no.	Туре	CRC ¹⁾	Weight	Part no.	Туре
[mm]		[g]				[g]		
40	1	122	174398	SNCS-40	4	239	2895921	CRSNCS-40
40 63	1 2	122 281	174398 174400	SNCS-40 SNCS-63	4	239 576	2895921 2895923	CRSNCS-40 CRSNCS-63

1) Corrosion resistance class CRC 1 to Festo standard FN 940070

Low corrosion stress. Dry internal application or transport and storage protection. Also applies to parts behind coverings, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions). Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment. Corrosion resistance class CRC 3 to Festo standard FN 940070

High corrosion stress. Outdoor exposure under moderate corrosive conditions. Externally visible parts with primarily functional surface requirements which are in direct contact with a normal industrial environment. Corrosion resistance class CRC 4 to Festo standard FN 940070

Particularly high corrosion stress. Outdoor exposure under extreme corrosive conditions. Parts exposed to aggressive media, e.g. in the chemical or food industries. Such applications may need to be safeguarded by special tests (ightarrow also FN 940082), using appropriate media.


NEW

Accessories

Swivel flange SNCL for DFLC

Material:

Die-cast aluminium



Dimensions and ordering data

For diam.	CD	E	EW	FL		L	MR
	Ø						
			-0.2				
[mm]	H10		-0.6	±0.2			
40	12	54 _{-0.5}	28	25		16	12
63	16	75 _{-0.6}	40	32		21	16
4.0.0	(0	41	27	20		89	483.3
100	60	41	27	20		09	405.5
100	60	41	27	20		09	+05.5
100 For diam.	60 TG	41	ХС	CRC ¹⁾	Weight	Part no.	Туре
		41			Weight [g]		
For diam.		41					
For diam. [mm]	TG	41	XC		[g]	Part no.	Туре

1) Corrosion resistance class CRC 1 to Festo standard FN 940070

Low corrosion stress. Dry internal application or transport and storage protection. Also applies to parts behind coverings, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions).


Cylinders with holding brake DFLC/G

Accessories

Swivel flange SNCB/SNCB-...-R3 for DFLC







Dimensions and ordering data

For diam.	CB	E	EK	FL	L	MR	TG	UB	XC
			ø						
[mm]	H14		H10/e8	±0.2		-0.5		h14	
40	28	54 _{-0.5}	12	25	16	12	38	52	344.7
40 63	28 40	54 _{-0.5} 75 _{-0.6}	1)		16 21	12 16	38 56.5	52 70	344.7 398.9

For diam.	Basic type				R3 – High co	rrosion protec	tion	
	CRC ¹⁾	Weight	Part no.	Туре	CRC ¹⁾	Weight	Part no.	Туре
[mm]		[g]				[g]		
40	1	155	174391	SNCB-40	3	151	176945	SNCB-40-R3
	-				1			
63	1	375	174393	SNCB-63	3	371	176947	SNCB-63-R3

1) Corrosion resistance class CRC 1 to Festo standard FN 940070


Low corrosion stress. Dry internal application or transport and storage protection. Also applies to parts behind coverings, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions). Corrosion resistance class CRC 3 to Festo standard FN 940070


High corrosion stress. Outdoor exposure under moderate corrosive conditions. Externally visible parts with primarily functional surface requirements which are in direct contact with a normal industrial environment.


NEW

Accessories

Swivel flange SNG for DFLG







Dimensions and ordering data

Dimensions	s allu oluelli	ig uala											
For diam.	CF	CG	СР	E	FL	L	SR	TG	XC	CRC ¹⁾	Weight	Part no.	Туре
[mm]	F7/h9	H14	d12	max.	±0.2		max.				[g]		
160	35	43	122	186	55	35	32	140 _{±0.3}	613	2	3577	152597	SNG-160


1) Corrosion resistance class CRC 2 to Festo standard FN 940070


Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

Swivel flange SNGL

Material: Die-cast aluminium

for DFLG





Dimensions and ordering data


Dimen	SIOIIS	and ordering	guala										
For dia	m.	CD	EW	E	FL	L	MR	TG	XC	CRC ¹⁾	Weight	Part no.	Туре
		ø											
[mm]		H9		±0.5	±0.2						[g]		
160		30	90.0.5/-1.2	179.5	55	35	25	140	613	2	2358	151534	SNGL-160

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

Accessories

Swivel flange SNGB for DFLG



1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

Accessories

Ordering data –	· Mounting attach	ments					Data sheets \rightarrow Internet: clevis for
Designation	For diam.	Part no.	Туре	Designation	For diam.	Part no.	Туре
Clevis foot LN/LI	NG			Clevis foot LBG ¹⁾ for DFLC			
$\overline{\bigcirc}$	40	33891	LNG-40	A	40	31762	LBG-40
SOL	63	33893	LNG-63		63	31764	LBG-63
C Kog	100	33895	LNG-100		100	31766	LBG-100
\sim	160	9037	LN-160				
Clevis foot LSNG	i			 Clevis foot LSN			
	40	31741	LSNG-40		40	5562	LSN-40
	63	31743	LSNG-63		63	5564	LSN-63
	100	31745	LSNG-100	0	100	5566	LSN-100
	160	152599	LSNG-160		160	6988	LSN-160

1) Suitable for ATEX

Ordering data – Mounting components, corrosion-resistant Data sheets → Internet:								
Designation	For diam.	Part no.	Туре					
Clevis foot CRLNG	Clevis foot CRLNG							
for DFLC								
\square	40	161841	CRLNG-40					
S Q	63	161843	CRLNG-63					
(9 pro	100	161845	CRLNG-100					

Ordering data –	Ordering data – Mounting components, high corrosion protection Data sheets → Internet: II							
Designation	For diam.	Part no.	Type ¹⁾					
Clevis foot LBG-R	Clevis foot LBG-R3							
for DFLC								
	40	2078792	LBG-40-R3					
	63	2078795	LBG-63-R3					
	100	2078799	LBG-100-R3					

1) Suitable for ATEX

Accessories Ordering data – Piston rod attachments Designation For diam. Part no. Туре Rod eye SGS 40 9262 SGS-M12x1.25 6 Ð' 63 9263 SGS-M16x1.5 ÌÒ 100 9264 SGS-M20x1.5 SGS-M36x2 160 10775 Rod clevis SG¹⁾ 40 6145 SG-M12x1.25 6 63 SG-M16x1.5 6146 100 6147 SG-M20x1.5 160 9581 SG-M36x2 Coupling piece KSG¹⁾ for DFLC 32964 KSG-M12x1.25 40 0 63 32965 KSG-M16x1.5 Ò KSG-M20x1.5 100 32966 ۲ 0

		Data sheets –	 Internet: piston rod attachment 					
Designation	For diam.	Part no.	Туре					
Rod clevis SGA ¹⁾	Rod clevis SGA ¹⁾							
	40	10767	SGA-M12x1.25					
	63	10768	SGA-M16x1.5					
	100	10769	SGA-M20x1.5					
	160	10771	SGA-M36x2					
Self-aligning rod	coupler FK ¹⁾							
	40	6141	FK-M12x1.25					
	63	6142	FK-M16x1.5					
SPP -	100	6143	FK-M20x1.5					
	160	10746	FK-M36x2					
			•					
	1							

1) Suitable for ATEX

Ordering data –	Piston-rod attachr	nents, corrosion-res	istant	Data sheets → Internet: p			→ Internet: piston rod attac		
Designation	For diam.	Part no.	Туре	Designation	For diam.	Part no.	Туре		
Rod eye CRSGS for DFLC				Rod clevis CRSG ¹ for DFLC	Rod clevis CRSG ¹⁾ for DFLC				
Ś	40	195583	CRSGS-M12x1.25		40	13570	CRSG-M12x1.25		
	63	195584	CRSGS-M16x1.5		63	13571	CRSG-M16x1.5		
Ó	100	195585	CRSGS-M20x1.5		100	13572	CRSG-M20x1.5		
Self-aligning rod of for DFLC					L.				
	40	2305779	CRFK-M12x1.25						
and the second	63	2490673	CRFK-M16x1.5						
	100	2545677	CRFK-M20x1.5						

1) Suitable for ATEX

Accessories

Proximity switches DADG

General technical data						
For diam.	40; 63	100	160			
Size	M4					
Type of mounting	Screwed on					
Type of installation	Flush					
Housing material	Steel					
Cable sheath material	TPE-U(PUR)					
Note on materials	Contains paint-wetting impairment substances					
	RoHS-compliant					
Product weight [g]	26	30	32			
Conforms to standard	EN 60947-5-2					
Certification	RCM compliance mark					
	c UL us (OL)					
CE marking (see declaration of conformity)	To EU EMC Directive					
Degree of protection	IP67					

Operating and environmental conditions

Operating and environmental con	ditions				
For diam.		40; 63	100	160	
Switching output		PNP			
Switching element function		N/O contact			
Electrical connection 1,		Cable			
connection type					
Electrical connection 1,		Open end			
connection technology					
Electrical connection 1,		3			
number of pins/wires					
Cable length	[m]	2			
Operating voltage range DC	[V]	10 30			
Max. switching frequency		5000 Hz			
Max. switching frequency DC		5000 Hz			
Max. output current	[mA]	100			
No-load supply current	[mA]	≤ 10			
Voltage drop	[V]	2			
Residual ripple	[%]	10			
Reverse polarity protection		For all electrical connect	tions		
Short circuit current rating		Pulsed			
Rated operating distance	[mm]	0.6			
Assured operating distance	[mm]	0.64			
Reduction factors		Aluminium = 0.55			
		Stainless steel St 18/8 =	= 0.8		
		Copper = 0.5			
		Brass = 0.65			
		Steel St 37 = 1.0			
Repetition accuracy	[mm]	0.01			
Ambient temperature	[°C]	-25 +70			

Ordering data Data sheets → Internet:					
	For diam.	Part no.	Туре		
	40; 63	8072857	DADG-D-F8-16/20		
Jane -	100	8072858	DADG-D-F8-25		
and the	160	8072859	DADG-D-F8-40		

Cylinders with holding brake DFLC/G

Accessories

Ordering data - Proximity switches for T-slot, magneto-resistive Data sheets → Internet: smt Cable length Part no. Type of mounting Switching Electrical connection Туре output [m] N/O contact Insertable in the slot from above, PNP Cable, 3-wire 2.5 574335 SMT-8M-A-PS-24V-E-2.5-OE flush with cylinder profile, Plug M8x1, 3-pin (AL) 0.3 574334 SMT-8M-A-PS-24V-E-0.3-M8D short design NPN Cable, 3-wire 2.5 574338 SMT-8M-A-NS-24V-E-2.5-OE Plug M8x1, 3-pin 0.3 574339 SMT-8M-A-NS-24V-E-0.3-M8D Non-contact-Plug, 2-wire 5 574341 SMT-8M-A-ZS-24V-E-5.0-0E-EX2 ing N/C contact Insertable in the slot from above, PNP Cable, 3-wire 7.5 574340 SMT-8M-A-PO-24V-E-7.5-OE AL BE flush with cylinder profile, short design Ordering data – Connecting cables Data sheets \rightarrow Internet: nebu Cable length Electrical connection, left Electrical connection, right Part no. Туре [m] 541333 NEBU-M8G3-K-2.5-LE3 Straight socket, M8x1, 3-pin Cable, open end, 3-wire 2.5 5 541334 NEBU-M8G3-K-5-LE3 Angled socket, M8x1, 4-pin Cable, open end, 3-wire 2.5 541338 NEBU-M8W3-K-2.5-LE3 5 541341 NEBU-M8W3-K-5-LE3

Data sheets → Internet: sdat

Accessories

Position transmitter

The position transmitter continuously senses the position of the piston.

It has an analogue output with an output signal in proportion to the piston position.

Ordering data – Position transmitter for T-slot

	Position measuring range	Analogue output [mA]	Type of mounting	Electrical connection	Cable length [m]	Part no.	Туре
	0 50	4 20	Insertable in the	Plug M8x1, 4-pin,	0.3	1531265	SDAT-MHS-M50-1L-SA-E-0.3-M8
E OT	0 80		slot from above	in-line		1531266	SDAT-MHS-M80-1L-SA-E-0.3-M8
	0100					1531267	SDAT-MHS-M100-1L-SA-E-0.3-M8
	0 125					1531268	SDAT-MHS-M125-1L-SA-E-0.3-M8
	0 160					1531269	SDAT-MHS-M160-1L-SA-E-0.3-M8

Ordering data – Sensor bracket for proximity switch SMT-8M and position transmitter SMAT-8M Data sheets → Internet: dasp for DFLG for DFLG For diam. Materials Part no. Type Image: The sensor bracket for proximity switch SMT-8M and position transmitter SMAT-8M Part no. Type Image: The sensor bracket for proximity switch SMT-8M and position transmitter SMAT-8M Part no. Type Image: The sensor bracket for proximity switch SMT-8M and position transmitter SMAT-8M Part no. Type

Ordering data -	Drdering data – Connecting cables Data sheets → Internet: :							
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part no.	Туре			
	Straight socket, M8x1, 4-pin	Cable, open end, 4-wire	2.5	541342	NEBU-M8G4-K-2.5-LE4			
STREET NO			5	541343	NEBU-M8G4-K-5-LE4			
and the second second	Angled socket, M8x1, 4-pin	Cable, open end, 4-wire	2.5	541344	NEBU-M8W4-K-2.5-LE4			
			5	541345	NEBU-M8W4-K-5-LE4			

Ordering data – One-way flow control valves Data sheets → Internet: grla Material Part no. Connection Туре Thread For tubing O.D. For exhaust air G1/8 4 Metal version 193143 GRLA-1/8-QS-4-D 6 GRLA-1/8-QS-6-D 193144 8 193145 GRLA-1/8-QS-8-D G1/4 6 193146 GRLA-1/4-QS-6-D 8 193147 GRLA-1/4-QS-8-D 10 193148 GRLA-1/4QS-10-D G3/8 6 193149 GRLA-3/8-QS-6-D 8 193150 GRLA-3/8-QS-8-D 10 193151 GRLA-3/8-QS-10-D G1/2 12 193152 GRLA-1/2-QS-12-D

Festo - Your Partner in Automation





1 Festo Inc.

5300 Explorer Drive Mississauga, ON L4W 5G4 Canada

Festo Customer Interaction Center Tel: 18774633786 Fax: 18773933786 Email: customer.service.ca@festo.com ventas.mexico@festo.com



2 Festo Pneumatic

Av. Ceylán 3, Col. Tequesquináhuac 54020 Tlalnepantla, Estado de México

Multinational Contact Center 01 800 337 8669



3 Festo Corporation 1377 Motor Parkway Suite 310 Islandia, NY 11749



4 **Regional Service Center** 7777 Columbia Road Mason, OH 45040

Festo Customer Interaction Center 1 800 993 3786 1 800 963 3786 customer.service.us@festo.com

Subject to change

f 🗾 in 🛗 www.festo.com/socialmedia

Connect with us



www.festo.com