


Proportional-pressure regulators VPPM

FESTO



Key features – Overview



- | | | | |
|----------------------------|--------------------------|--|--|
| [1] LED displays | [5] Sub-base valve | [9] Compressed air supply at both ends | [11] Individual valve |
| [2] Display window | [6] Exhaust at both ends | [10] H-rail mounting | [12] Angle bracket can be rotated 180° during mounting |
| [3] Control elements | [7] Working ports | | |
| [4] Plug socket with cable | [8] Manifold block | | |

Innovative

- Multi-sensor control (cascade control)
- Diagnostics
- Choice of regulation characteristic
- Temperature compensated
- High dynamic response
- High repetition accuracy
- Processing of modular products
- IO-Link, for direct connection to a higher-level IO-Link/I-Port master

Flexible

- Individual valves (in-line valve)
- Sub-base valves (battery/sub-base valve)
- Various user interfaces
 - LED displays
 - LCD display
 - Adjustment/selection buttons
- Choice of valves with different pressure ranges
- Pressure range can be modified on the valve
- Choice of different setpoint specifications
 - Current input
 - Voltage input

Operational safety


- Integrated pressure sensor with separate output
- Wire break monitoring
- Pressure maintained if controller fails

Easy to install

- Manifold block (manifold)
- H-rail mounting
- Individually via mounting bracket
- QS fittings

Key features – Overview


Overview, VPPM IO-Link



- [1] Diagnostics via fieldbus
- [2] Bus node
- [3] Electrical connection block CAPC
- [4] Connecting cable NEBU
- [5] Proportional-pressure regulator VPPM with IO-Link

Key features – VPPM on valve terminal MPA-S

Overview, VPPM on the valve terminal MPA-S



[1] 24 V

[2] Serial data

Innovative

- Multi-sensor control
- Diagnostics via the bus
- Choice of regulation characteristic
- High dynamic response
- 2 accuracy levels

Flexible

- For all common protocols
- As an individual pressure regulator
- As a pressure zone regulator
- Choice of 3 valves with different pressure ranges
- 3 pressure ranges (presets) can be set via the bus
- Internal or external compressed air supply possible

Operational safety

- Long service life
- LED display for the operating status
- Pressure maintained in case of supply voltage failure
- Fast troubleshooting with LEDs on the valves and diagnostics via fieldbus
- Ease of servicing with replaceable valves

Easy to install

- Easy replacement of the valves
- Tested units
- Easy extension of the valve terminal


Note

More information on the VPPM valves for MPA-S

→ mpas

Key features – Control loop

Layout of a control loop



Design

The figure shows a closed loop control. The reference variable w (setpoint value, e.g. 5 V or 8 mA) initially acts on a comparator. The measuring equipment sends the controlled variable x value (actual value, e.g. 3 bar) to the comparator as a feedback signal r . The closed-loop control element detects the system deviation e and actuates the final control element. The output of the final control element acts on the


controlled system. The closed-loop control element thus attempts to compensate for the difference between the reference variable w and the controlled variable x by using the final control element.

Method of operation

This process runs continuously so changes in the reference variable are always detected. However, a system deviation will also occur if the reference variable is constant and the controlled variable changes. This happens when the flow through the valve changes in response to a switching operation, a cylinder movement or a load change. The disturbance variable z will also cause a system deviation. An

example of this is when the pressure drops in the air supply. The disturbance variable z acts on the controlled variable x in an unforeseen way. In all cases, the closed-loop controller attempts to correct the controlled variable x to the reference variable w .

Multi-sensor control (cascade control) of the VPPM



Cascade controller

Unlike conventional direct-acting controls, in multi-sensor controls multiple control loops are nested inside one other. The overall controlled system is divided into smaller sub-sections that

are easier to control for the specific task.


Control precision

Control accuracy and dynamic response are greatly improved with the multi-sensor control principle in comparison with a single-acting regulator.

Key features – Control loop


Terms related to the proportional-pressure regulator

Hysteresis




There is always a linear relationship within a certain tolerance between the setpoint value entered and the pressure output. Nevertheless, it makes a difference whether the setpoint value is entered as rising or falling. The difference between the maximum deviations is referred to as hysteresis.

Response sensitivity




The response sensitivity of the device determines how sensitively one can change, i.e. adjust, a pressure. The smallest setpoint value difference that results in a change in the output pressure is referred to as the response sensitivity.
In this case, 0.01 bar.

Linearity error




A perfectly linear progression of the control characteristic of the output pressure is theoretical. The maximum percentage deviation from this theoretical control characteristic is referred to as the linearity error. The percentage value refers to the maximum output pressure. (full scale)

Repetition accuracy (reproducibility)




The repetition accuracy is the margin within which the fluid output variables are scattered when the same electrical input signal coming from the same direction is repeatedly adjusted. The repetition accuracy is expressed as a percentage of the maximum fluid output signal.

Zero point offset




If, for example, a VPPM cannot be exhausted for safety reasons, the minimum pressure can be increased from the zero point. The smallest setpoint value is then assigned an output pressure of 5 bar, for example, and the largest setpoint value an output pressure of 10 bar. Zero point suppression is automatically switched off if the zero point offset is used.

Pressure range adaptation



In the delivery status, 100% setpoint value corresponds to 100% of the fluid output signal. Pressure range adaptation or adjustment enables the fluid output variable to be matched to the setpoint value.

Zero point suppression




In real-world applications, it is possible for there to be a residual voltage or residual current at the setpoint input of the VPPM via the setpoint generator. Zero point suppression is used so the valve is reliably exhausted at a setpoint value of zero.

Key features – Flow rate

Flow rate q_n of 1 → 2 as a function of excess output pressure p_2


VPPM-6L/F-...-0L2H-...

(2 bar)




VPPM-6L/F-...-0L6H-...

(6 bar)



VPPM-6L/F-...-0L10H-...

(10 bar)





Flow rate q_n of 2 → 3 as a function of excess output pressure p_2

VPPM-6L/F-...-0L2H-...

(2 bar)


VPPM-6L/F-...-0L6H-...

(6 bar)



VPPM-6L/F-...-0L10H-...


(10 bar)




Proportional-pressure regulators VPPM

Key features – Flow rate


Flow rate q_n of 1 → 2 as a function of excess output pressure p_2
VPPM-8L...-0L2H... (2 bar)




VPPM-8L...-0L6H... (6 bar)




VPPM-8L...-0L10H... (10 bar)



VPPM-8L...-0L6H... (6 bar)



VPPM-8L...-0L6H... (6 bar)




VPPM-8L...-0L10H... (10 bar)




Key features – Flow rate


Flow rate q_n of 1 → 2 as a function of excess output pressure p_2
VPPM-8F/8TA-...-0L2H-... (2 bar)



VPPM-8F/8TA-...-0L6H-... (6 bar)




VPPM-8F/8TA-...-0L10H-... (10 bar)




Flow rate q_n of 2 → 3 as a function of excess output pressure p_2
VPPM-8F/8TA-...-0L2H-... (2 bar)


VPPM-8F/8TA-...-0L6H-... (6 bar)



VPPM-8F/8TA-...-0L6H-... (6 bar)




VPPM-8F/8TA-...-0L10H-... (10 bar)




Proportional-pressure regulators VPPM

Key features – Flow rate


Flow rate q_n of 1 → 2 as a function of excess output pressure p_2
VPPM-12L-...-0L2H-... (4 bar)




VPPM-12L-...-0L6H-... (8 bar)




VPPM-12L-...-0L10H-... (11 bar)



VPPM-12L-...-0L2H-... (4 bar)





VPPM-12L-...-0L6H-... (8 bar)





VPPM-12L-...-0L10H-... (11 bar)



Product range overview


Function	Version	Design	Pneumatic port 1, 2, 3	Nominal width pressurisation/exhaust [mm]	Pressure regulation range [MPa] [bar]	Setpoint value input			→ Page/ Internet					
						Voltage type	Current type	Digital						
Pressure regulators	Operator unit with LED (standard)			 Piloted diaphragm valve	G1/8	6/4.5 0.002 ... 0.2 0.006 ... 0.6 0.01 ... 1	0.02 ... 2 0.06 ... 6 0.1 ... 10	■	■	-	18			
					Sub-base	6/4.5 0.002 ... 0.2 0.006 ... 0.6 0.01 ... 1	0.02 ... 2 0.06 ... 6 0.1 ... 10	■	■	-				
					8/7	0.002 ... 0.2 0.006 ... 0.6 0.01 ... 1	0.02 ... 2 0.06 ... 6 0.1 ... 10	■	■	-				
					G1/4	8/7 0.002 ... 0.2 0.006 ... 0.6 0.01 ... 1	0.02 ... 2 0.06 ... 6 0.1 ... 10	■	■	-				
					G1/2	1 2/12 0.002 ... 0.2 0.006 ... 0.6 0.01 ... 1	0.02 ... 2 0.06 ... 6 0.1 ... 10	■	■	-				
	Operator unit with LED, for IO-Link			 Piloted diaphragm valve	G1/8	6/4.5 0.002 ... 0.2 0.006 ... 0.6 0.01 ... 1	0.02 ... 2 0.06 ... 6 0.1 ... 10	-	-	■	26			
					Sub-base	6/4.5 0.002 ... 0.2 0.006 ... 0.6 0.01 ... 1	0.02 ... 2 0.06 ... 6 0.1 ... 10	-	-	■				
					8/7	0.002 ... 0.2 0.006 ... 0.6 0.01 ... 1	0.02 ... 2 0.06 ... 6 0.1 ... 10	-	-	■				
					G1/4	8/7 0.002 ... 0.2 0.006 ... 0.6 0.01 ... 1	0.02 ... 2 0.06 ... 6 0.1 ... 10	-	-	■				
					G1/2	1 2/12 0.002 ... 0.2 0.006 ... 0.6 0.01 ... 1	0.02 ... 2 0.06 ... 6 0.1 ... 10	-	-	■				

Product range overview

Function	Version	Design	Pneumatic port 1, 2, 3	Nominal width pressurisation/exhaust [mm]	Pressure regulation range [MPa] [bar]	Setpoint value input			→ Page/ Internet	
						Voltage type	Current type	Digital		
Pressure regulators										
	Operator unit with LCD, pressure unit variable	Piloted diaphragm valve	G1/8	6/4.5	0.002 ... 0.2 0.006 ... 0.6 0.01 ... 1	0.02 ... 2 0.06 ... 6 0.1 ... 10	■	■	-	18
			Sub-base	6/4.5	0.002 ... 0.2 0.006 ... 0.6 0.01 ... 1	0.02 ... 2 0.06 ... 6 0.1 ... 10	■	■	-	
				8/7	0.002 ... 0.2 0.006 ... 0.6 0.01 ... 1	0.02 ... 2 0.06 ... 6 0.1 ... 10	■	■	-	
			G1/4	8/7	0.002 ... 0.2 0.006 ... 0.6 0.01 ... 1	0.02 ... 2 0.06 ... 6 0.1 ... 10	■	■	-	
			G1/2	1 2/12	0.002 ... 0.2 0.006 ... 0.6 0.01 ... 1	0.02 ... 2 0.06 ... 6 0.1 ... 10	■	■	-	
Operator unit with LED, for valve terminal MPA-S										
	Piloted diaphragm valve	Sub-base MPA	6/4.5, 8/7	0.002 ... 0.2 0.006 ... 0.6 0.01 ... 1	0.02 ... 2 0.06 ... 6 0.1 ... 10	-	-	■	mpas	

Peripherals overview

Individual valve VPPM-6L ... , VPPM-8L ...




Accessories

	Description	→ Page/Internet
[1]	Proportional-pressure regulator VPPM	Operator unit with LED, IO-Link 26
[2]	Connecting cable NEBU-M12G5...	– 41
[3]	Proportional-pressure regulator VPPM	Operator unit with LED 40
[4]	Plug socket with cable, angled NEBU-M12W8...	– 40
[5]	Proportional-pressure regulator VPPM	Operator unit with LCD 18
[6]	Straight plug socket with cable SIM-M12-8GD...	– 18
[7]	Push-in fitting QS	For connecting tubing with standard O.D. qs
[8]	Silencer	For fitting in exhaust ports u
[9]	Bracket VAME-P1-A	For mounting the valve 37
[10]	H-rail mounting VAME-P1-T	For mounting on an H-rail 38

Peripherals overview


Individual valve VPPM-12L ...



Accessories	Description	→ Page/Internet
[1]	Proportional-pressure regulator VPPM	Operator unit with LED, IO-Link 26
[2]	Connecting cable NEBU-M12G5-...	– 41
[3]	Retaining screws	–
[4]	Proportional-pressure regulator VPPM	Operator unit with LED or LCD 18
[5]	Push-in fitting QS	For connecting tubing with standard O.D. qs
[6]	Silencer	For fitting in exhaust ports u
[7]	Angled plug socket with cable NEBU-M12W8-...	– 40
[8]	Straight plug socket with cable SIM-M12-8GD-...	– 40

Peripherals overview


Valve manifold assembly with VPPM-6F ... , VPPM-8F ...



Accessories		Description	→ Page/Internet
[1]	Angled plug socket with cable NEBU-M12W8...	–	40
[2]	Straight plug socket with cable SIM-M12-8GD...	–	40
[3]	Proportional-pressure regulator VPPM	Operator unit with LED	18
[4]	Proportional-pressure regulator VPPM	Operator unit with LCD	18
[5]	Proportional-pressure regulator VPPM	Operator unit with LED, IO-Link	26
[6]	Connecting cable NEBU-M12G5...	–	41
[7]	Blanking plug B	–	b
[8]	Push-in fitting QS	For connecting tubing with standard O.D.	qs
[9]	Silencer	For fitting in exhaust ports	u
[10]	Cover plate VABB-P1	For vacant position; seal and countersunk screws included in the scope of delivery	36
	Manifold block VABM	–	35

System overview

VPPM-6TA ... , VPPM-8TA ... for valve terminal MPA-S



Accessories		Description	→ Page/Internet
[1]	Valve terminal MPA-S	With fieldbus interface and VPPM	mpas
[2]	Proportional-pressure regulator VPPM	For valve terminal MPA-S	mpas
[3]	Electrical linking module VMPA1-FB-EV-AB	For sub-base of the proportional-pressure regulator	mpas
[4]	Sub-base VMPA-FB-AP-P1	Without electrical linking module or electrical module	mpas
[5]	Push-in fitting QS	–	qs
[6]	Mounting VMPA-BG	–	mpas

Type codes

001	Series		009	Upper pressure value of control range
VPPM	Proportional pressure regulator, modular		2H	2 bar
002	Nominal width [mm]		6H	6 bar
6	6		10H	10 bar
8	8			
12	12			
003	Directional control valve type		010	Alternative lower pressure regulation range
L	In-line valve		...L	0 ... 9 bar
F	Flanged valve			
T	Flanged valve for valve terminal			
004	Mounting method		011	Alternative upper pressure regulation range
	Standard		...H	0.2 ... 10 bar
A	Valve terminal MPA		012	Setpoint input for individual valves
005	Dynamic response			For valve terminals/servo-pneumatics
L	Low		V1	0 ... 10 V
006	Valve function		LK	IO-Link®
1	3/2-way valve, normally closed		A4	4 ... 20 mA
007	Pneumatic connection		013	Switching input/output
G18	G1/8			None
G14	G1/4		N	NPN
G12	G1/2		P	PNP
F	Flange/sub-base		014	Overall accuracy
008	Lower pressure value of control range			2%
0L	0 bar		S1	1 %
			015	Operator unit/interface
				None
			C1	With LCD, variable pressure unit

Proportional-pressure regulators VPPM

Datasheet – VPPM with analogue interface

-  - Flow rate
380 ... 7000 l/min
-  - Voltage
21.6 ... 26.4 V DC
-  - Pressure regulation range
0.002 ... 1 MPa
0.02 ... 10 bar

Variants

- Setpoint input as analogue voltage signal 0 ... 10 V
- Setpoint input as analogue current signal 4 ... 20 mA
- LED version
- With LCD display (... C1)
- Switching output NPN (N) or PNP (P)



General technical data

Type	VPPM-6	VPPM-8	VPPM-12	Sub-base		
Pneumatic port	G1/8	G1/4	G1/2	Via sub-base		
Valve function	3-way proportional-pressure regulator					
Design	Piloted diaphragm regulator					
Sealing principle	Soft					
Actuation type	Electrical					
Type of control	Piloted					
Reset method	Mechanical spring					
Type of mounting	Via through-hole, via accessories					
Mounting position	Any					
Nominal width	Pressurisation [mm]	6	8	12	6	8
	Exhaust port [mm]	4.5	7	12	4.5	7
Standard nominal flow rate	[l/min]	→ Graphs				
Product weight	[g]	400	560	2050	400	560

Electrical data

Type	VPPM-6	VPPM-8	VPPM-12	
Electrical connection	Plug, round design, 8-pin, M12			
Operating voltage range	[V DC]	24 ± 10% = 21.6 ... 26.4		
Residual ripple	[%]	10		
Duty cycle	[%]	100		
Max. electrical power consumption	[W]	7	7	12
Setpoint input signal	Voltage [V DC]	0 ... 10		
	Current [mA]	4 ... 20		
Short circuit current rating		For all electrical connections		
Reverse polarity protection		For all electrical connections		
Degree of protection		IP65		

Note

Output pressure will be unregulated if the power supply cable is interrupted.

Datasheet – VPPM with analogue interface

Operating and environmental conditions				
Pressure regulation range		[MPa]	0.002 ... 0.2	0.006 ... 0.6
		[bar]	0.02 ... 2	0.06 ... 6
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]		
		Inert gases		
Note on the operating/pilot medium		Lubricated operation not possible		
Input pressure 1 ¹⁾	[MPa]	0 ... 0.4	0 ... 0.8	0... 1.1
	[bar]	0 ... 4	0 ... 8	0... 11
Max. pressure hysteresis	[mbar]	10	30	50
Hysteresis	[%]	0.5 FS		
Linearity	[%]	1 FS		
Linearity error FS (full scale)	[%]	2		
Reproducibility	[%]	0.5 FS		
Overall accuracy	[%]	1.25 FS		
Repetition accuracy FS (full scale)	[%]	0.5		
Temperature coefficient	[%/K]	0.04		
Ambient temperature, operator unit LED (standard)	[°C]	0 ... 60		
Ambient temperature, operator unit with LCD	[°C]	0 ... 50		
Temperature of medium	[°C]	10 ... 50		
Note on materials		RoHS-compliant		
PWIS conformity		VDMA24364-B1/B2-L		
Corrosion resistance class	[CRC]	2 ²⁾		
CE marking (see declaration of conformity)		To EU EMC Directive (see declaration of conformity) ³⁾		
		To EU RoHS Directive ³⁾		
UKCA marking (see declaration of conformity)		To UK instructions for EMC ³⁾		
		To UK RoHS instructions ³⁾		
Certification		RCM		
		c UL us listed (OL)		
Certificate-issuing authority		UL E322346		

1) Input pressure 1 should always be 1 bar greater than the maximum regulated output pressure.

2) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

3) For information about the area of use, see the EC declaration of conformity at: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/) → Support/Downloads.



If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Datasheet – VPPM with analogue interface

Materials

Sectional view VPPM-6 ..., VPPM-8 ...


Sectional view VPPM-12 ...



[1]	Housing	Wrought aluminium alloy
[2]	Diaphragm	Nitrile rubber


Datasheet – VPPM with analogue interface

Pin allocation M12, electrical connection	
Pin	Function
1	Digital input D1
2	+24 V DC supply voltage
3	Analogue input W-
4	Analogue input W+
5	Digital input D2
6	Analogue output X
7	0 V DC or GND
8	Digital output D3



Version

Circuit symbol



- Piloted diaphragm valve
- Pressure regulation range:
0.002 ... 0.2, 0.006 ... 0.6,
0.01 ... 1 MPa
- Signal setpoint value input:
0 ... 10 V DC, 4 ... 20 mA


Proportional-pressure regulators VPPM

Datasheet – VPPM with analogue interface

Dimensions

VPPM-6F, sub-base valve

Download CAD data → www.festo.com
with LCD



[1] Socket head screw M4x65


Type	B1	B2	D2 ∅	D4 ∅	D5 ∅	H1	H2	H3	H4	H5	H8	H9	H10	H11
VPPM-6F	65.4	47.5	M12x1	4.4	6	126.9	110.4	80.1	52.8	41.3	28.3	26.3	23	12.2

Type	L1	L2	L3	L4	L5	L6
VPPM-6F	41.5	31.5	30.3	28.4	12.3	25

Dimensions

VPPM-6L, pneumatic port G1/8

Download CAD data → www.festo.com
with LCD




Type	B1	B2	B3	D1 ∅	D2 ∅	D4 ∅	H1	H2	H3	H4	H6	H7	H9	H10	H12
VPPM-6L	65.5	47.5	16	G1/8	M12x1	4.4	126.9	110.4	80.1	52.8	42	27	26.3	23	12

Type	L1	L2	L6
VPPM-6L	41.5	31.5	25

Datasheet – VPPM with analogue interface

Dimensions

VPPM-8F, sub-base valve

Download CAD data → www.festo.com
with LCD


[1] Socket head screw M4x77

Type	B1	B2	D2	D5 ∅	H1	H2	H3	H4	H5	H8	H9	H10	H11
VPPM-8F	77.4	59.5	M12x1	8	126.9	110.4	80	52.8	41.3	28.3	26.3	23	12.2

Type	L1	L2	L3	L4	L5	L6
VPPM-8F	41.5	31.5	29.3	28.4	12.3	25

Dimensions

VPPM-8L, pneumatic port G1/4

Download CAD data → www.festo.com
with LCD

Type	B1	B2	B3	D1	D2	H1	H2	H3	H4	H6	H7	H9	H10	H12
VPPM-8L	77.4	59.5	22	G1/4	M12x1	126.9	110.4	80	52.8	42	27	26.3	23	12

Type	L1	L2	L6
VPPM-8L	47	31.5	25


Proportional-pressure regulators VPPM

Datasheet – VPPM with analogue interface

Dimensions

VPPM-6TA, sub-base valve

Download CAD data → www.festo.com



[1] Socket head screw M4x55


Type	B1	D5 Ø	H2	H3	H4	H5	H8	H9	H11
VPPM-6TA	55.1	6	110.4	95.5	52.8	41.3	28.3	26.3	12.2

Type	L1	L2	L3	L4	L5	L6
VPPM-6TA	41.5	31.5	30.3	28.4	12.3	9.9

Dimensions

VPPM-8TA, sub-base valve with LCD

Download CAD data → www.festo.com



[1] Socket head screw M4x77

Type	B1	D5 Ø	H2	H3	H4	H5	H8	H9	H10	H11	H13
VPPM-8TA	77.4	8	110.4	80	52.8	41.3	28.3	26.3	23	12.2	95.5


Type	L1	L2	L3	L4	L5	L6	L7
VPPM-8TA	41.5	31.5	29.3	28.4	12.3	25	9.9

Datasheet – VPPM with analogue interface

Dimensions

VPPM-12L, pneumatic port G1/2

Download CAD data → www.festo.com
with LCD



Type	B1	B2	B3	B4	D1	D2	D4 ∅	H1	H2	H3	H4	H6	H7	H9	H10	H12	H13
VPPM-12L	107.4	89.5	36	74	G1/2	M12x1	5.5	162.8	146.3	116	78.2	63	38.5	33.2	23	16.5	35.9

Type	L1	L2	L6	L7
VPPM-12L	72	53	25	9.5

Datasheet – VPPM with IO-Link interface

-  Flow rate
380 ... 7000 l/min
-  Voltage
18 ... 30 V DC
-  Pressure regulation range
0.002 ... 1 MPa
0.02 ... 10 bar
- Digital setpoint and actual value transfer
- For connection to an I/O-Link/I-Port master
- LED version
- Comparator output (digital)



General technical data		VPPM-6	VPPM-8	VPPM-12	Sub-base	
Pneumatic port		G1/8	G1/4	G1/2	Via sub-base	
Valve function		3-way proportional-pressure regulator				
Design		Piloted diaphragm regulator				
Display type		LED				
Sealing principle		Soft				
Actuation type		Electrical				
Type of control		Piloted				
Reset method		Mechanical spring				
Type of mounting		Via through-hole, via accessories				
Mounting position		Any				
Nominal width	Pressurisation	[mm]	6	8	12	
	Exhaust port	[mm]	4.5	7	12	
Standard nominal flow rate	[l/min]		→ Graphs			
Product weight	[g]	400	560	2050	400	
IO-Link	Protocol		IO-Link, I-Port			
	Protocol version		Device V1.1			
	Port type		A			
	Process data width OUT	[byte]	2			
	Process data width IN	[byte]	2			
Communication mode	COM1	[kBaud]	4.8			
	COM2	[kBaud]	38.4			
	COM3	[kBaud]	230.4			
IO-Link	Minimum cycle time	[ms]	0.5			
Information on materials	Housing		Wrought aluminium alloy			

Electrical data		VPPM-6	VPPM-8	VPPM-12
Type				
Electrical connection		M12 plug connector, 5-pin		
Operating voltage range	[V DC]	18 ... 30		
Max. current consumption	[mA]	300	300	500
Max. electrical power consumption	[W]	7		12
Short circuit current rating		For all electrical connections		
Reverse polarity protection		For all electrical connections		
Residual ripple	[%]	10		
Duty cycle	[%]	100		
Degree of protection		IP65		

-  Note

Output pressure will be unregulated if the power supply cable is interrupted.

Datasheet – VPPM with IO-Link interface

Operating and environmental conditions			
Pressure regulation range	[MPa]	0.002 ... 0.2	0.006 ... 0.6
	[bar]	0.02 ... 2	0.06 ... 6
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium		Inert gases	
Input pressure 1 ¹⁾	[MPa]	0 ... 0.4	0 ... 0.8
	[bar]	0 ... 4	0 ... 8
Max. pressure hysteresis	[mbar]	10	30
Hysteresis	[%]	0.5 FS	
Linearity	[%]	1 FS	
Linearity error FS (full scale)	[%]	1	
Reproducibility	[%]	0.5 FS	
Overall accuracy	[%]	1.25 FS	
Repetition accuracy FS (full scale)	[%]	0.5	
Temperature coefficient	[%/K]	0.04	
Ambient temperature	[°C]	0 ... 60	
Temperature of medium	[°C]	10 ... 50	
Note on materials		RoHS-compliant	
PWIS conformity		VDMA24364-B1/B2-L	
Corrosion resistance class	[CRC]	2 ²⁾	
CE marking (see declaration of conformity)		To EU EMC Directive (see declaration of conformity) ³⁾	
		To EU RoHS Directive ³⁾	
UKCA marking (see declaration of conformity)		To UK instructions for EMC ³⁾	
		To UK RoHS instructions ³⁾	
Certification		RCM	
Certificate-issuing authority		c UL us listed (OL)	
		UL E322346	

1) Input pressure 1 should always be 1 bar greater than the maximum regulated output pressure.

2) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.


3) For information about the area of use, see the EC declaration of conformity at: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/) → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Pin allocation of IO-Link interface			
	Pin	Allocation	Function
	1	24 V DC ($U_{EL/SEN}$)	Operating voltage supply (PS)
	2	n.c.	Not connected
	3	0 V DC ($U_{EL/SEN}$)	Operating voltage supply (PS)
	4	C/Q I-Port	Data communication
	5	n.c.	Not connected
	-	FE	Functional earth

Version

Circuit symbol



- Piloted diaphragm valve
- Pressure regulation range: 0.002 ... 0.2, 0.006 ... 0.6, 0.01 ... 1 MPa
- Signal setpoint value input: 0 ... 10 V DC, 4 ... 20 mA


Proportional-pressure regulators VPPM, IO-Link

Datasheet – VPPM with IO-Link interface

Dimensions

VPPM-6F, sub-base valve

Download CAD data → www.festo.com



[1] Socket head screw M4x65


Type	B1	B2	D2 Ø	D5 Ø	H1	H2	H4	H5	H8	H9	H11
VPPM-6F	65.5	47.5	M12x1	6	126.9	110.4	52.8	41.3	28.3	26.3	12.2

Type	L1	L2	L3	L4	L5	W1 ± 5°
VPPM-6L	41.5	31.5	30.3	28.4	12.3	45°

Dimensions

VPPM-6L, pneumatic port G1/8

Download CAD data → www.festo.com




Type	B1	B2	B3	D1 Ø	D2 Ø	D4 Ø	H1	H2	H4	H6	H7	H9	H12
VPPM-6L	65.5	47.5	16	G1/8	M12x1	4.4	126.9	110.4	52.8	42	27	26.3	12

Type	L1	L2	W1 ± 5°
VPPM-6L	41.5	31.5	45°

Datasheet – VPPM with IO-Link interface

Dimensions

VPPM-8F, sub-base valve

Download CAD data → www.festo.com


[1] Socket head screw M4x7

Type	B1	B2	D2	D5 Ø	H1	H2	H4	H5	H8	H9	H11
VPPM-8L	77.4	59.5	M12x1	8	126.9	110.4	52.8	41.3	28.3	26.3	12.2

Type	L1	L2	L3	L4	L5	W1 ± 5°
VPPM-8L	41.5	31.5	29.3	28.4	12.3	45°

Dimensions

VPPM-8L, pneumatic port G1/4

Download CAD data → www.festo.com

Type	B1	B2	B3	D1	D2	H1	H2	H4	H6	H7	H9	H12
VPPM-8L	77.4	59.5	22	G1/4	M12x1	126.9	110.4	52.8	42	27	26.3	12


Type	L1	L2	W1 ± 5°
VPPM-8L	47	31.5	45°

Datasheet – VPPM with IO-Link interface

Dimensions

VPPM-12L, pneumatic port G1/2

Download CAD data → www.festo.com



Type	B1	B2	B3	B4	D1	D2	D4 Ø	H1	H2	H4	H6	H7	H9	H12	H13
VPPM-12L	107.4	89.5	36	74	G1/2	M12x1	4.4	162.8	146.3	78.2	63	38.5	33.2	16.5	35.9

Type	L1	L2	L7	W1 ±5°
VPPM-12L	72	53	9.5	45°

Datasheet

Ordering data		Pneumatic port	Pressure regulation range		Part no.	Type
VPPM with analogue interface		1, 2, 3	[MPa]	[bar]		
Voltage type 0 ... 10 V						
Overall accuracy 2%	G1/8	0.002 ... 0.2	0.02 ... 2	542233	VPPM-6L-L-1-G18-0L2H-V1N	
		0.006 ... 0.6	0.06 ... 6	542234	VPPM-6L-L-1-G18-0L6H-V1N	
				554043	VPPM-6L-L-1-G18-0L6H-V1P	
				558337	VPPM-6L-L-1-G18-0L6H-V1P-C1	
				558346	VPPM-6L-L-1-G18-0L6H-V1N-C1	
	G1/8	0.01 ... 1	0.1 ... 10	575125	VPPM-6L-L-1-G18-0L10H-V1P-C1	
				542235	VPPM-6L-L-1-G18-0L10H-V1N	
				554044	VPPM-6L-L-1-G18-0L10H-V1P	
	Sub-base	0.002 ... 0.2	0.02 ... 2	542245	VPPM-6F-L-1-F-0L2H-V1N	
		0.006 ... 0.6	0.06 ... 6	542246	VPPM-6F-L-1-F-0L6H-V1N	
				558339	VPPM-6F-L-1-F-0L6H-V1P-C1	
				558347	VPPM-6F-L-1-F-0L6H-V1N-C1	
				571285	VPPM-8F-L-1-F-0L6H-V1P	
		0.01 ... 1	0.1 ... 10	542247	VPPM-6F-L-1-F-0L10H-V1N	
	G1/4	0.006 ... 0.6	0.06 ... 6	571296	VPPM-8L-L-1-G14-0L6H-V1P	
Overall accuracy 1%	G1/8	0.002 ... 0.2	0.02 ... 2	542227	VPPM-6L-L-1-G18-0L2H-V1N-S1	
		0.006 ... 0.6	0.06 ... 6	542228	VPPM-6L-L-1-G18-0L6H-V1N-S1	
				554039	VPPM-6L-L-1-G18-0L6H-V1P-S1	
				571448	VPPM-6L-L-1-G18-0L6H-V1N-S1C1	
				575121	VPPM-6L-L-1-G18-0L6H-V1P-S1C1	
		0.01 ... 1	0.1 ... 10	542229	VPPM-6L-L-1-G18-0L10H-V1N-S1	
				554040	VPPM-6L-L-1-G18-0L10H-V1P-S1	
				558335	VPPM-6L-L-1-G18-0L10H-V1P-S1C1	
				558345	VPPM-6L-L-1-G18-0L10H-V1N-S1C1	
	Sub-base	0.002 ... 0.2	0.02 ... 2	542239	VPPM-6F-L-1-F-0L2H-V1N-S1	
		0.006 ... 0.6	0.06 ... 6	542240	VPPM-6F-L-1-F-0L6H-V1N-S1	
				571286	VPPM-8F-L-1-F-0L6H-V1P-S1	
				571287	VPPM-8F-L-1-F-0L6H-V1P-S1C1	
		0.01 ... 1	0.1 ... 10	542241	VPPM-6F-L-1-F-0L10H-V1N-S1	
	G1/4	0.01 ... 1	0.1 ... 10	571291	VPPM-8L-L-1-G14-0L10H-V1N-S1	
				571292	VPPM-8L-L-1-G14-0L10H-V1P-S1	
				571293	VPPM-8L-L-1-G14-0L10H-V1P-S1C1	
		0.006 ... 0.6	0.06 ... 6	571294	VPPM-8L-L-1-G14-0L6H-V1N-S1	
				571295	VPPM-8L-L-1-G14-0L6H-V1N-S1C1	
				571297	VPPM-8L-L-1-G14-0L6H-V1P-S1	
				571298	VPPM-8L-L-1-G14-0L6H-V1P-S1C1	
	G1/2	0.01 ... 1	0.1 ... 10	575235	VPPM-12L-L-1-G12-0L10H-V1N-S1	
				575236	VPPM-12L-L-1-G12-0L10H-V1P-S1	
				575237	VPPM-12L-L-1-G12-0L10H-V1P-S1C1	
		0.006 ... 0.6	0.06 ... 6	575238	VPPM-12L-L-1-G12-0L6H-V1N-S1	
				575239	VPPM-12L-L-1-G12-0L6H-V1N-S1C1	
				575240	VPPM-12L-L-1-G12-0L6H-V1P-S1	
				575241	VPPM-12L-L-1-G12-0L6H-V1P-S1C1	

Datasheet

Ordering data		Pneumatic port	Pressure regulation range		Part no.	Type	
VPPM with analogue interface	1, 2, 3		[MPa]	[bar]			
Current type 4 ... 20 mA							
Overall accuracy 2%	G1/8	0.002 ... 0.2	0.02 ... 2	542236	VPPM-6L-L-1-G18-0L2H-A4N		
			0.06 ... 6	542237	VPPM-6L-L-1-G18-0L6H-A4N		
				554045	VPPM-6L-L-1-G18-0L6H-A4P		
				558338	VPPM-6L-L-1-G18-0L6H-A4P-C1		
		0.01 ... 1	0.1 ... 10	542238	VPPM-6L-L-1-G18-0L10H-A4N		
	Sub-base	0.002 ... 0.2	0.02 ... 2	542248	VPPM-6F-L-1-F-0L2H-A4N		
			0.06 ... 6	542249	VPPM-6F-L-1-F-0L6H-A4N		
				558340	VPPM-6F-L-1-F-0L6H-A4P-C1		
		0.01 ... 1	0.1 ... 10	571282	VPPM-8F-L-1-F-0L6H-A4P		
	G1/4	0.006 ... 0.6	0.06 ... 6	542250	VPPM-6F-L-1-F-0L10H-A4N		
				571299	VPPM-8L-L-1-G14-0L6H-A4P		
Overall accuracy 1%	G1/8	0.002 ... 0.2	0.02 ... 2	542230	VPPM-6L-L-1-G18-0L2H-A4N-S1		
			0.06 ... 6	542231	VPPM-6L-L-1-G18-0L6H-A4N-S1		
				554041	VPPM-6L-L-1-G18-0L6H-A4P-S1		
		0.01 ... 1	0.1 ... 10	575128	VPPM-6L-L-1-G18-0L6H-A4P-S1C1		
		0.002 ... 0.2	0.02 ... 2	542232	VPPM-6L-L-1-G18-0L10H-A4N-S1		
			0.06 ... 6	554042	VPPM-6L-L-1-G18-0L10H-A4P-S1		
				558336	VPPM-6L-L-1-G18-0L10H-A4P-S1C1		
	Sub-base	0.002 ... 0.2	0.02 ... 2	542242	VPPM-6F-L-1-F-0L2H-A4N-S1		
			0.06 ... 6	542243	VPPM-6F-L-1-F-0L6H-A4N-S1		
				571283	VPPM-8F-L-1-F-0L6H-A4P-S1		
		0.01 ... 1	0.1 ... 10	571284	VPPM-8F-L-1-F-0L6H-A4P-S1C1		
		0.01 ... 1	0.1 ... 10	542244	VPPM-6F-L-1-F-0L10H-A4N-S1		
	G1/4		0.1 ... 10	571288	VPPM-8L-L-1-G14-0L10H-A4N-S1		
				571289	VPPM-8L-L-1-G14-0L10H-A4P-S1		
				571290	VPPM-8L-L-1-G14-0L10H-A4P-S1C1		
	0.006 ... 0.6	0.06 ... 6	571302	VPPM-8L-L-1-G14-0L6H-A4N-S1			
			571303	VPPM-8L-L-1-G14-0L6H-A4N-S1C1			
			571300	VPPM-8L-L-1-G14-0L6H-A4P-S1			
			571301	VPPM-8L-L-1-G14-0L6H-A4P-S1C1			
	G1/2	0.01 ... 1	0.1 ... 10	575232	VPPM-12L-L-1-G12-0L10H-A4N-S1		
				575233	VPPM-12L-L-1-G12-0L10H-A4P-S1		
				575234	VPPM-12L-L-1-G12-0L10H-A4P-S1C1		
		0.006 ... 0.6	0.06 ... 6	575242	VPPM-12L-L-1-G12-0L6H-A4P-S1		
				575243	VPPM-12L-L-1-G12-0L6H-A4P-S1C1		
				575244	VPPM-12L-L-1-G12-0L6H-A4N-S1		
				575245	VPPM-12L-L-1-G12-0L6H-A4N-S1C1		
For valve terminal							
Overall accuracy 2%	Via valve terminal	0.002 ... 0.2	0.02 ... 2	542220	VPPM-6TA-L-1-F-0L2H		
				572410	VPPM-8TA-L-1-F-0L2H-C1		
				542221	VPPM-6TA-L-1-F-0L6H		
				572411	VPPM-8TA-L-1-F-0L6H-C1		
		0.002 ... 0.2	0.02 ... 10	542222	VPPM-6TA-L-1-F-0L10H		
				572412	VPPM-8TA-L-1-F-0L10H-C1		
Overall accuracy 1%	Via valve terminal	0.002 ... 0.2	0.02 ... 2	542217	VPPM-6TA-L-1-F-0L2H-S1		
				572407	VPPM-8TA-L-1-F-0L2H-S1C1		
				542218	VPPM-6TA-L-1-F-0L6H-S1		
		0.002 ... 0.2	0.02 ... 10	572408	VPPM-8TA-L-1-F-0L6H-S1C1		
				542219	VPPM-6TA-L-1-F-0L10H-S1		
				572409	VPPM-8TA-L-1-F-0L10H-S1C1		

Datasheet

Ordering data		Pneumatic port	Pressure regulation range		Part no.	Type
VPPM with IO-Link interface		1, 2, 3	[MPa]	[bar]		
Overall accuracy 1%	G1/8		0.002 ... 0.2	0.02 ... 2	8024258	VPPM-6L-L-1-G18-0L2H-LK-S1
			0.006 ... 0.6	0.06 ... 6	8024259	VPPM-6L-L-1-G18-0L6H-LK-S1
			0.01 ... 1	0.1 ... 10	8024260	VPPM-6L-L-1-G18-0L10H-LK-S1
	Sub-base		0.002 ... 0.2	0.02 ... 2	8031107	VPPM-6F-L-1-F-0L2H-LK-S1
			0.006 ... 0.6	0.06 ... 6	8031108	VPPM-6F-L-1-F-0L6H-LK-S1
			0.01 ... 1	0.1 ... 10	8031109	VPPM-6F-L-1-F-0L10H-LK-S1
	G1/4		0.002 ... 0.2	0.02 ... 2	8024261	VPPM-8L-L-1-G14-0L2H-LK-S1
			0.006 ... 0.6	0.06 ... 6	8024262	VPPM-8L-L-1-G14-0L6H-LK-S1
			0.01 ... 1	0.1 ... 10	8024263	VPPM-8L-L-1-G14-0L10H-LK-S1
	Sub-base		0.002 ... 0.2	0.02 ... 2	8031110	VPPM-8F-L-1-F-0L2H-LK-S1
			0.006 ... 0.6	0.06 ... 6	8031111	VPPM-8F-L-1-F-0L6H-LK-S1
			0.01 ... 1	0.1 ... 10	8031112	VPPM-8F-L-1-F-0L10H-LK-S1
	G1/2		0.002 ... 0.2	0.02 ... 2	8024264	VPPM-12L-L-1-G12-0L2H-LK-S1
			0.006 ... 0.6	0.06 ... 6	8024265	VPPM-12L-L-1-G12-0L6H-LK-S1
			0.01 ... 1	0.1 ... 10	8024266	VPPM-12L-L-1-G12-0L10H-LK-S1

Ordering data – Modular product system


Ordering table			Conditions	Code	Enter code
Size	6				
Module no.	543432				
Design	Modular pressure regulator			VPPM	
Nominal width	6			-6	
	8			-8	
	12	[1]		-12	
Valve type	In-line	[2]		L	
	Flanged valve	[3]		F	
	Flanged valve for valve terminal	[4]		T	
Dynamic response	Low dynamic response (pilot-actuated, soft-sealing)			-L	
Valve operating mode	3/2-way valve, normally closed			-1	
Connection type	G thread G1/8			-G18	
	G thread G1/4			-G14	
	G thread G1/2			-G12	
	Flange/sub-base			-F	
Pressure regulation range	0 ... 2 bar			-OL2H	
	0 ... 6 bar			-OL6H	
	0 ... 10 bar			-OL10H	
Alternative lower pressure regulation range	0.1 ... 10 bar	[5]		...L	
Alternative upper pressure regulation range	0.1 ... 10 bar	[5]		...H	
Setpoint specification	Voltage (standard 0 ... 10 V)			-V1	
	IO-Link			-LK	
	Current (standard 4 ... 20 mA)			-A4	
Switching output	PNP - switching			P	
	NPN - switching			N	
Overall accuracy	1%			-S1	
Operator unit	with LCD, pressure unit, variable			C1	

- 1) 12 Only with valve type L(in-line)
 2) L Only with connection type G18, G14, G12 (G thread G1/8, G1/4, G1/2)
 3) F Only with connection type F (flange/sub-base)
 4) T Only with connection type F (flange/sub-base)
 5) ...L Not with pressure regulation range (OL2H, OL6H, OL10H).
 Must always be less than alternative upper pressure regulation range H
 5) ...H Not with pressure regulation range (OL2H, OL6H, OL10H).
 Must always be greater than alternative upper pressure regulation range L

Accessories


Manifold block VABM-P1

Material:
Wrought aluminium alloy



Dimensions

Download CAD data → www.festo.com



Type	B1	D1	D2	D3	D4	D5	H1	H2	H3	H4	H5
VABM-P1-SF-G14-2-P3	30.2	G1/2	G1/4	17.8	11	6.2	~116	50	34.5	15.5	7.5
VABM-P1-SF-G14-3-P3											
VABM-P1-SF-G14-4-P3											

Type	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10
VABM-P1-SF-G14-2-P3	113	96	42							
VABM-P1-SF-G14-3-P3	155	138	84	110.4	42	27	14	31.7	14.4	8.5
VABM-P1-SF-G14-4-P3	197	180	126							

Dimensions and ordering data							
Valve positions	L1	L2	L3	Weight [g]	CRC ¹⁾	Part no.	Type
2	113	96	42	900	2	542252	VABM-P1-SF-G14-2-P3
3	155	138	84	1230	2	542253	VABM-P1-SF-G14-3-P3
4	197	180	126	1565	2	542254	VABM-P1-SF-G14-4-P3

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.


Note

In combination with manifold block VABM-P1- ... flanged valves VPPM-6F- ... and VPPM-8F- ... are to be used.

Accessories


Cover plate
VABB-P1

Material:
Wrought aluminium alloy, NBR, steel



Dimensions

Download CAD data → www.festo.com



Type	B1	H1	H2	H3	L1	L2
VABB-P1	5	56	26.5	5.2	41.5	31.5

Ordering data		Part no.	Type
Weight [g]	CRC		
35	1 ¹⁾	558350	VABB-P1


1) Corrosion resistance class CRC 1 to Festo standard FN 940070

Low corrosion stress. Dry indoor application or transport and storage protection. Also applies to parts behind covers, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions).

Accessories


Bracket
VAME-P1-A

Material:
Wrought aluminium alloy, steel



Dimensions

Download CAD data → www.festo.com



[1] Socket head screw M4

[2] Proportional-pressure regulator
VPPM

[3] Bracket can be rotated if
required

Type	B1	B2	B3	B4	D1 ∅	H1	H2	H3	H4	H5	H6	L1	L2	L3
VAME-P1-A	41	22	8	3	4.5	70	88.6	70	66.4	38.3	9.5	55	45	5

Ordering data

Weight [g]	CRC	Part no.	Type
71	1 ¹⁾	542251	VAME-P1-A

1) Corrosion resistance class CRC 1 to Festo standard FN 940070

Low corrosion stress. Dry indoor application or transport and storage protection. Also applies to parts behind covers, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions).




Note

In combination with bracket VAME-P1-A in-line valves VPPM-6L... and VPPM-8L... are to be used.

Accessories


H-rail mounting VAME-P1-T

Material:
Wrought aluminium alloy, steel



Dimensions

Download CAD data → www.festo.com



[1] Socket head screw M4

[2] Proportional-pressure regulator
VPPM

[3] H-rail NRH

[4] H-rail mounting can be rotated
180° if required

Type	B1	B2	B3	H1	H2	H3	H4	H5	H6	H7	L1	L2	L3	L4	L5	L6
VAME-P1-T	20.7	20	10	71.2	60	90.3	66.9	49.1	33.7	7.2	55	34	31.5	15.75	13	8

Ordering data	CRC	Part no.	Type
Weight [g] 150	1) 1)	542255	VAME-P1-T

1) Corrosion resistance class CRC 1 to Festo standard FN 940070


Low corrosion stress. Dry indoor application or transport and storage protection. Also applies to parts behind covers, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions).

 **Note**
In combination with H-rail VAME-P1-T in-line valves VPPM-6L-... and VPPM-8L-... are to be used.

Accessories


Connecting cable NEBV-M12G8-KD-3-M12G4

For connecting the proportional-pressure regulator VPPM to the analogue input and output modules of the CPX terminal.



Dimensions and pin allocation

Download CAD data → www.festo.com



[1] Straight socket, 8-pin, to VPPM

[2] Straight plug, 4-pin, to CPX modules

Type	B1	B2	B3	D1 ∅	D2 ∅	H1	H2	H3	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10
NEBV-M12G8-...	38.8	20.5	13.8	6.3	3.2	18.8	16.3	9.4	2500	500	44.9	41.7	17.5	15	15	13.3	7.1	3.6


Proportional-pressure regulators VPPM

Accessories

Connecting cable


NEBV-M12G8-K-5-M12G4

For connecting the proportional-pressure regulator VPPM to the analogue output modules of the CPX terminal.



Dimensions and pin allocation

Download CAD data → www.festo.com



Type	L1	L2	L3
NEBV-M12G8-K-2-M12G4	2000	44.9	41.7
NEBV-M12G8-K-5-M12G4	5000	44.9	41.7

Ordering data	Description	Part no.	Type
Datasheets → Internet: connecting cable			
Connecting cable			
	Straight socket, 8-pin, M12	2 m 5 m 10 m	525616 525618 570008
	Angled socket, 8-pin, M12	2 m 5 m 10 m	542256 542257 570007
	One straight socket, 8-pin, and one straight plug, 4-pin	2 m 5 m	553575 553576
	One straight socket, 8-pin, and two straight plugs, 4-pin		547888
Datasheets → Internet: mpz			
Setpoint module	Setpoint module for generating 6 + 1 analogue voltage signals	546224	MPZ-1-24DC-SGH-6-SW5

Accessories

Ordering data IO-Link		Description	Part no.	Type
Connecting cable				
	Straight socket, M12x1, 5-pin, degree of protection IP65, IP68, IP69K	5 m	574321	NEBU-M12G5-E-5-Q8N-M12G5
		7.5 m	574322	NEBU-M12G5-E-7.5-Q8N-M12G5
		10 m	574323	NEBU-M12G5-E-10-Q8N-M12G5