

Standard cylinders DNCB, ISO 15552

FESTO



- 2 - Type discontinued
Available up until 2012

Standard cylinders DNCB, ISO 15552

Features

FESTO

At a glance



- Standards-based cylinders to ISO 15552 (corresponds to the withdrawn standards ISO 6431, DIN ISO 6431, VDMA 24 562, NF E 49 003.1 and UNI 10290)

- The modern design and construction saves up to 11% on space compared to ordinary standard cylinders, thus permitting a considerably more compact system design



DIN



High quality product

- Proven technology, compact, solid and reliable
- Excellent running characteristics thanks to efficient piston system
- Simple and sensitive adjustable end-position cushioning thanks to new PPV adjusting screw
- When an ideal setting has been found, the imprinted scale ensures easy reproducibility


Contactless sensing

- The proximity sensors fit flush in the profile slot. On the one hand, this does away with the need for additional mounting kits and on the other, it protects the proximity sensor against mechanical damage

Easy to assemble

- Large selection of mounting options
- All accessories and mounting attachments from the DNC range can be used

Accessories



Guide units protect ISO standard cylinders from torsion when these are subjected to high torque loads. They provide high precision guidance for workpiece handling and other handling applications.

Standard cylinders DNCB, ISO 15552

Type codes


		DNCB	–	50	–	80	–	PPV	–	A
Type										
Double-acting										
DNCB	Standard cylinder									
Piston Ø [mm]										
Stroke [mm]										
Cushioning										
PPV	Pneumatic cushioning adjustable at both ends									
Sensing										
A	For proximity sensing									

- 1 - Type discontinued
Available up until 2012

Standard cylinders DNCB, ISO 15552

Peripherals overview

FESTO



Standard cylinders DNCB, ISO 15552

Peripherals overview

FESTO

Mounting attachments and accessories		
	Brief description	→ Page/Internet
1 Multi-position kit DPNC	for connecting two DNCB cylinders with identical piston $\varnothing$ to form a multi-position cylinder	10
2 Foot mounting HNC	for bearing and end caps corresponds to MS1 to ISO 15552	11
3 Flange mounting FNC	for bearing or end caps corresponds to MF1/MF2 to ISO 15552	11
4 Trunnion flange ZNCF	for bearing or end caps	12
5 Trunnion support LNZG	corresponds to MT4 to ISO 15552	14
6 Swivel flange SNC	for end caps	14
7 Clevis foot LSNG	with spherical bearing	16
8 Clevis foot LSNSG	weld-on with spherical bearing	16
9 Swivel flange SNCS	with spherical bearing for end caps	15
10 Clevis foot LBG	with non-rotating pivot pin	16
11 Swivel flange SNCL	for end caps corresponds to MP4 to ISO 15552	16
12 Swivel flange SNCB	for end caps corresponds to MP2 to ISO 15552	15
13 Clevis foot LNG	for swivel flange SNCB	16
14 Clevis foot LSN	with spherical bearing	16
15 Trunnion mounting kit ZNCM	for mounting anywhere on the cylinder barrel corresponds to MT4 to ISO 15552	13
16 Rod eye SGS	with spherical bearing	17
17 Right-angle clevis foot LQG	with non-rotating pivot pin for rod eye SGS	16
18 Rod clevis SGA	suitable for spherical mounting of cylinders in conjunction with rod eye SGS	17
19 Coupling piece KSG	for compensating radial deviations	17
20 Rod clevis SG	permits a swivelling movement of the cylinder in one plane	17
21 Self-aligning rod coupler FK	for compensating radial and angular deviations	17
22 Guide unit FENG	to protect against torsion at high torque loads	18
24 Slot cover ABP-5-S	to protect the sensor cable and keep dirt out of the sensor slots	19
25 Proximity sensors SME/SMT-8	can be integrated in the cylinder profile barrel	19
26 One-way flow control valve GRLA	for speed regulation	17
27 Push-in fitting QS	for connecting compressed air tubing with standard O.D.	quick star


- 1 - Type discontinued
Available up until 2012

Standard cylinders DNCB, ISO 15552

Technical data

FESTO

Function



DIN



www.festo.com/en/Spare_parts_servi



- N- Diameter
32 ... 100 mm
- T- Stroke length
2 ... 2,000 mm

Wearing parts kits

→ 9

General technical data						
Piston Ø	32	40	50	63	80	100
Pneumatic connection	G $\frac{1}{8}$	G $\frac{1}{4}$	G $\frac{1}{4}$	G $\frac{3}{8}$	G $\frac{3}{8}$	G $\frac{1}{2}$
Piston rod thread	M10x1.25	M12x1.25	M16x1.5	M16x1.5	M20x1.5	M20x1.5
Constructional design	Piston					
	Piston rod					
	Profile barrel					
Cushioning	Pneumatic cushioning adjustable at both ends					
Cushioning length [mm]	20	20	22	22	32	32
Position sensing	For proximity sensing					
Type of mounting	Using internal threads					
	With accessories					
Mounting position	Any					

Operating and environmental conditions	
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:4:4]
Note on operating/pilot medium	Operation with lubricated medium possible (in which case lubricated operation will always be required)
Operating pressure [bar]	0.6 ... 12
Ambient temperature ¹⁾ [°C]	-20 ... +80
Corrosion resistance class CRC ²⁾	2

1) Note operating range of proximity sensors

2) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents

Forces [N] and impact energy [J]						
Piston Ø	32	40	50	63	80	100
Theoretical force at 6 bar, advancing	483	754	1,178	1,870	3,016	4,712
Theoretical force at 6 bar, retracting	415	633	990	1,682	2,721	4,418
Max. impact energy at end positions	0.4	0.7	1	1.3	2	3

Note

Sizing software

Pro Pneu


→ www.festo.com

Standard cylinders DNCB, ISO 15552

Technical data

FESTO


Lateral force F_q as a function of stroke length l



Weights [g]						
Piston Ø	32	40	50	63	80	100
Product weight with 0 mm stroke	460	760	1,225	1,800	3,135	4,575
Additional weight per 10 mm stroke	27	37	56	62	92	101
Moving load with 0 mm stroke	108	204	363	460	800	1,045
Additional load per 10 mm stroke	9	16	25	25	39	39

Materials

Sectional view



Standard cylinder		
1	Cylinder barrel	Anodised aluminium
2	Bearing/end caps	Die-cast aluminium
3	Piston rod	High-alloy steel
4	Flange screws	Galvanised steel
-	Seals	Polyurethane, nitrile rubber
-	Note on material	Free of copper, PTFE and silicone

- 2 - Type discontinued
Available up until 2012


Standard cylinders DNCB, ISO 15552

Technical data

FESTO

Dimensions

Download CAD Data → www.festo.com/us/cad



Ø [mm]	AM	B Ø d11	BG	E	EE	J2	J3	KK	L1	L2	L7
32	22	30	16	45	G $\frac{1}{8}$	5.25	5.7	M10x1.25	18	94	6.5
40	24	35	16	54	G $\frac{1}{4}$	8	4	M12x1.25	21.3	105	7.5
50	32	40	17	64	G $\frac{1}{4}$	8	5.5	M16x1.5	26.8	106	9.5
63	32	45	17	75	G $\frac{3}{8}$	12.75	6.25	M16x1.5	27	121	9
80	40	45	17	93	G $\frac{3}{8}$	12.5	8	M20x1.5	34.2	128	11
100	40	55	17	110	G $\frac{1}{2}$	13.5	10	M20x1.5	38	138	7.5

Ø [mm]	MM Ø	PL	RT	TG	VA	VD	WH	ZJ	1	2	3
32	12	19.5	M6	32.5	4	4	26	120	10	16	6
40	16	22.5	M6	38	4	4	30	135	13	18	6
50	20	22.5	M8	46.5	4	4	37	143	17	24	8
63	20	27.5	M8	56.5	4	4	37	158	17	24	8
80	25	30	M10	72	4	4	46	174	22	30	6
100	25	31.5	M10	89	4	4	51	189	22	30	6

 Type discontinued
Available up until 2012

Standard cylinders DNCB, ISO 15552

Technical data

FESTO

Ordering data											
Stroke [mm]		Part No.	Type	Stroke [mm]		Part No.	Type	Stroke [mm]		Part No.	Type
		Piston Ø 32 mm				Piston Ø 40 mm				Piston Ø 50 mm	
25		532 724	DNCB-32-25-PPV-A	25		532 737	DNCB-40-25-PPV-A	25		532 750	DNCB-50-25-PPV-A
40		532 725	DNCB-32-40-PPV-A	40		532 738	DNCB-40-40-PPV-A	40		532 751	DNCB-50-40-PPV-A
50		532 726	DNCB-32-50-PPV-A	50		532 739	DNCB-40-50-PPV-A	50		532 752	DNCB-50-50-PPV-A
80		532 727	DNCB-32-80-PPV-A	80		532 740	DNCB-40-80-PPV-A	80		532 753	DNCB-50-80-PPV-A
100		532 728	DNCB-32-100-PPV-A	100		532 741	DNCB-40-100-PPV-A	100		532 754	DNCB-50-100-PPV-A
125		532 729	DNCB-32-125-PPV-A	125		532 742	DNCB-40-125-PPV-A	125		532 755	DNCB-50-125-PPV-A
160		532 730	DNCB-32-160-PPV-A	160		532 743	DNCB-40-160-PPV-A	160		532 756	DNCB-50-160-PPV-A
200		532 731	DNCB-32-200-PPV-A	200		532 744	DNCB-40-200-PPV-A	200		532 757	DNCB-50-200-PPV-A
250		532 732	DNCB-32-250-PPV-A	250		532 745	DNCB-40-250-PPV-A	250		532 758	DNCB-50-250-PPV-A
320		532 733	DNCB-32-320-PPV-A	320		532 746	DNCB-40-320-PPV-A	320		532 759	DNCB-50-320-PPV-A
400		532 734	DNCB-32-400-PPV-A	400		532 747	DNCB-40-400-PPV-A	400		532 760	DNCB-50-400-PPV-A
500		532 735	DNCB-32-500-PPV-A	500		532 748	DNCB-40-500-PPV-A	500		532 761	DNCB-50-500-PPV-A
Stroke [mm]		Piston Ø 63 mm		Stroke [mm]		Piston Ø 80 mm		Stroke [mm]		Piston Ø 100 mm	
25		532 763	DNCB-63-25-PPV-A	25		532 884	DNCB-80-25-PPV-A	25		532 897	DNCB-100-25-PPV-A
40		532 764	DNCB-63-40-PPV-A	40		532 885	DNCB-80-40-PPV-A	40		532 898	DNCB-100-40-PPV-A
50		532 765	DNCB-63-50-PPV-A	50		532 886	DNCB-80-50-PPV-A	50		532 899	DNCB-100-50-PPV-A
80		532 766	DNCB-63-80-PPV-A	80		532 887	DNCB-80-80-PPV-A	80		532 900	DNCB-100-80-PPV-A
100		532 767	DNCB-63-100-PPV-A	100		532 888	DNCB-80-100-PPV-A	100		532 901	DNCB-100-100-PPV-A
125		532 768	DNCB-63-125-PPV-A	125		532 889	DNCB-80-125-PPV-A	125		532 902	DNCB-100-125-PPV-A
160		532 769	DNCB-63-160-PPV-A	160		532 890	DNCB-80-160-PPV-A	160		532 903	DNCB-100-160-PPV-A
200		532 770	DNCB-63-200-PPV-A	200		532 891	DNCB-80-200-PPV-A	200		532 904	DNCB-100-200-PPV-A
250		532 771	DNCB-63-250-PPV-A	250		532 892	DNCB-80-250-PPV-A	250		532 905	DNCB-100-250-PPV-A
320		532 772	DNCB-63-320-PPV-A	320		532 893	DNCB-80-320-PPV-A	320		532 906	DNCB-100-320-PPV-A
400		532 773	DNCB-63-400-PPV-A	400		532 894	DNCB-80-400-PPV-A	400		532 907	DNCB-100-400-PPV-A
500		532 774	DNCB-63-500-PPV-A	500		532 895	DNCB-80-500-PPV-A	500		532 908	DNCB-100-500-PPV-A

Ordering data – Variable stroke			
Piston Ø [mm]	Stroke [mm]	Part No.	Type
32	2 ... 2,000	532 723	DNCB-32-...-PPV-A
40	2 ... 2,000	532 736	DNCB-40-...-PPV-A
50	2 ... 2,000	532 749	DNCB-50-...-PPV-A
63	3 ... 2,000	532 762	DNCB-63-...-PPV-A
80	3 ... 2,000	532 883	DNCB-80-...-PPV-A
100	3 ... 2,000	532 896	DNCB-100-...-PPV-A

Ordering data – Wearing parts kits ¹⁾		
Piston Ø [mm]	Part No.	Type
32	665 294	DNCB-32-PPV-A
40	665 295	DNCB-40-PPV-A
50	665 296	DNCB-50-PPV-A
63	665 297	DNCB-63-PPV-A
80	665 298	DNCB-80-PPV-A
100	665 299	DNCB-100-PPV-A

1) Assembly grease included in scope of delivery

Standard cylinders DNCB, ISO 15552

Accessories

FESTO



Multi-position kit DPNC

Material:

Flange: Wrought aluminium alloy
threaded pins, hex nuts: Galvanised steel

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data						
For Ø	F1	ZJ	Max. overall stroke length	Weight	Part No.	Type
[mm]			[mm]	[g]		
32	27	120	1,000	85	174 418	DPNC-32
40	27	135	1,000	115	174 419	DPNC-40
50	32	143	1,000	210	174 420	DPNC-50
63	28	158	1,000	360	174 421	DPNC-63
80	38	174	1,000	620	174 422	DPNC-80
100	38	189	1,000	1,190	174 423	DPNC-100

Note

The maximum overall stroke length may not be exceeded when combining cylinders and the multi-position kit.

Connecting two cylinders with identical piston Ø as a 3 or 4-position cylinder.

A 3 or 4-position cylinder consists of two separate cylinders whose piston rods advance in opposing directions.


Depending upon actuation and stroke pattern, this type of cylinder can assume up to four positions. In each

case the cylinder is driven precisely against a stop. If one end of the piston rod is fixed, the cylinder barrel

executes the movement. The cylinder must be connected with flexible line connections.


Implementing 3 positions

Two cylinders with identical stroke length must be connected to this end.



Implementing 4 positions

Two cylinders with different stroke lengths must be connected to this end.




Standard cylinders DNCB, ISO 15552

FESTO

Accessories

Foot mounting HNC

Material:
Galvanised steel
Free of copper and PTFE




Dimensions and ordering data													
For Ø	AB Ø	AH	AO	AT	AU	SA	TR	US	XA	XS	CRC ¹⁾	Weight [g]	Part No. Type
[mm]													
32	7	32	6.5	4	24	142	32	45	144	45	2	144	174 369 HNC-32
40	10	36	9	4	28	161	36	54	163	53	2	193	174 370 HNC-40
50	10	45	9.5	5	32	170	45	64	175	62	2	353	174 371 HNC-50
63	10	50	12.5	5	32	185	50	75	190	63	2	436	174 372 HNC-63
80	12	63	15	6	41	210	63	93	215	81	2	829	174 373 HNC-80
100	14.5	71	17.5	6	41	220	75	110	230	86	2	1,009	174 374 HNC-100

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents

Flange mounting FNC

Material:
Galvanised steel
Free of copper and PTFE
RoHS-compliant



Dimensions and ordering data												
For Ø	E	FB Ø	MF	R	TF	UF	W	ZF	CRC ¹⁾	Weight	Part No.	Type
[mm]		H13								[g]		
32	45	7	10	32	64	80	16	130	1	221	174 376	FNC-32
40	54	9	10	36	72	90	20	145	1	291	174 377	FNC-40
50	65	9	12	45	90	110	25	155	1	536	174 378	FNC-50
63	75	9	12	50	100	120	25	170	1	679	174 379	FNC-63
80	93	12	16	63	126	150	30	190	1	1,495	174 380	FNC-80
100	110	14	16	75	150	175	35	205	1	2,041	174 381	FNC-100

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents

Standard cylinders DNCB, ISO 15552

Accessories

FESTO


Trunnion flange ZNCF

Material:

Corrosion resistant cast steel

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data												
For Ø	C2	C3	TD Ø e9	TK	TL	TM	US	XH	XL	CRC ¹⁾	Weight [g]	Part No. Type
[mm]												
32	71	86	12	16	12	50	45	18	128	2	130	174 411 ZNCF-32
40	87	105	16	20	16	63	54	20	145	2	240	174 412 ZNCF-40
50	99	117	16	24	16	75	64	25	155	2	390	174 413 ZNCF-50
63	116	136	20	24	20	90	75	25	170	2	600	174 414 ZNCF-63
80	136	156	20	28	20	110	93	32	188	2	1,150	174 415 ZNCF-80
100	164	189	25	38	25	132	110	32	208	2	2,030	174 416 ZNCF-100

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents

Standard cylinders DNCB, ISO 15552


Accessories

FESTO

Trunnion mounting kit ZNCM

The mounting kit can be attached at any position along the profile of the cylinder barrel.

Material:
Tempered steel
Free of copper and PTFE



Dimensions and ordering data							
For Ø	B1	C2	C3	TD Ø e9	TL	TM	UW
[mm]							
32	30	71	86	12	12	50	65
40	32	87	105	16	16	63	75
50	34	99	117	16	16	75	95
63	41	116	136	20	20	90	105
80	44	136	156	20	20	110	130
100	48	164	189	25	25	132	145

For Ø	XG	XJ	XV	Max. tightening torque [Nm]	CRC ¹⁾	Weight [g]	Part No.	Type
[mm]								
32	69	73	77	4 +1	2	224	163 525	ZNCM-32
40	79	82.5	86	8 +1	2	396	163 526	ZNCM-40
50	87	90	93	8 +2	2	616	163 527	ZNCM-50
63	98	97.5	100	18 +2	2	931	163 528	ZNCM-63
80	111	110	109	28 +2	2	1,494	163 529	ZNCM-80
100	123	120	117	28 +2	2	2,095	163 530	ZNCM-100

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents

Standard cylinders DNCB, ISO 15552

Accessories

FESTO

LNZG trunnion support

Material:


Trunnion support:

Anodised aluminium

Plain bearing: Plastic

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data														
For Ø	CR	DA	FK	FN	FS	H1	HB	KE	NH	TH	UL	CRC ¹⁾	Weight	Part No. Type
[mm]	Ø	Ø	Ø				Ø			±0.2			[g]	
32	12	11	15	30	10.5	15	6.6	6.8	18	32	46	2	90	32 959 LNZG-32
40, 50	16	15	18	36	12	18	9	9	21	36	55	2	140	32 960 LNZG-40/50
63, 80	20	18	20	40	13	20	11	11	23	42	65	2	190	32 961 LNZG-63/80
100	25	20	25	50	16	24.5	14	13	28.5	50	75	2	320	32 962 LNZG-100/125

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents


Swivel flange SNC

Material:

Die-cast aluminium

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data										
For Ø	CG	CP	EK	FL	L	SR	XC	CRC ¹⁾	Weight	Part No. Type
[mm]	H14	h14	Ø	±0.2					[g]	
32	14	34	10	22	13	10	142	2	90	174 383 SNC-32
40	16	40	12	25	16	12	160	2	120	174 384 SNC-40
50	21	45	16	27	16	12	170	2	240	174 385 SNC-50
63	21	51	16	32	21	16	190	2	320	174 386 SNC-63
80	25	65	20	36	22	16	210	2	625	174 387 SNC-80
100	25	75	20	41	27	20	230	2	830	174 388 SNC-100

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents

Standard cylinders DNCB, ISO 15552

FESTO

Accessories


Swivel flange SNCB

Material:

Die-cast aluminium

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data												
For Ø	CB	EK	FL	L	ML	MR	UB	XC	CRC ¹⁾	Weight	Part No.	Type
[mm]	H14	Ø e8	±0.2				h14			[g]		
32	26	10	22	13	55	8.5	45	142	2	103	174 390	SNCB-32
40	28	12	25	16	63	12	52	160	2	155	174 391	SNCB-40
50	32	12	27	16	71	12	60	170	2	232	174 392	SNCB-50
63	40	16	32	21	83	16	70	190	2	375	174 393	SNCB-63
80	50	16	36	22	103	16	90	210	2	636	174 394	SNCB-80
100	60	20	41	27	127	20	110	230	2	1035	174 395	SNCB-100

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring higher corrosion resistance. External visible parts in direct contact with industrial atmospheres or media such as solvents and cleaning agents, with a predominantly functional requirement for the surface



Swivel flange SNCS

Material:

Die-cast aluminium

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data											
For Ø	CN Ø	EP	EX	FL	LT	MS	XC	CRC ¹⁾	Weight	Part No.	Type
[mm]		±0.2		±0.2					[g]		
32	10	10.5	14	22	13	15	142	2	85	174 397	SNCS-32
40	12	12	16	25	16	17	160	2	125	174 398	SNCS-40
50	16	15	21	27	18	20	170	2	210	174 399	SNCS-50
63	16	15	21	32	21	22	190	2	280	174 400	SNCS-63
80	20	18	25	36	22	27	210	2	540	174 401	SNCS-80
100	20	18	25	41	27	29	230	2	700	174 402	SNCS-100

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring higher corrosion resistance. External visible parts in direct contact with industrial atmospheres or media such as solvents and cleaning agents, with a predominantly functional requirement for the surface

Standard cylinders DNCB, ISO 15552

Accessories

FESTO



Swivel flange SNCL

Material:

Die-cast aluminium

Free of copper and PTFE

RoHS-compliant



Dimensions and ordering data									
For Ø	CD	EW	FL	L	MR	XC	CRC ¹⁾	Weight	Part No. Type
[mm]	Ø							[g]	
32	10	26	22	13	10	142	2	75	174 404 SNCL-32
40	12	28	25	16	12	160	2	100	174 405 SNCL-40
50	12	32	27	16	12	170	2	160	174 406 SNCL-50
63	16	40	32	21	16	190	2	250	174 407 SNCL-63
80	16	50	36	22	16	210	2	405	174 408 SNCL-80
100	20	60	41	27	20	230	2	655	174 409 SNCL-100

1) Corrosion resistance class 2 according to Festo standard 940 070


Components requiring higher corrosion resistance. External visible parts in direct contact with industrial atmospheres or media such as solvents and cleaning agents, with a predominantly functional requirement for the surface

Ordering data – Mounting attachments				Technical data → Internet: clevis foot			
Designation	For Ø	Part No.	Type	Designation	For Ø	Part No.	Type
Clevis foot LSNG				Weld-on clevis foot LSNSG			
	32	31 740	LSNG-32		32	31 747	LSNSG-32
	40	31 741	LSNG-40		40	31 748	LSNSG-40
	50	31 742	LSNG-50		50	31 749	LSNSG-50
	63	31 743	LSNG-63		63	31 750	LSNSG-63
	80	31 744	LSNG-80		80	31 751	LSNSG-80
	100	31 745	LSNG-100		100	31 752	LSNSG-100
Clevis foot LBG				Clevis foot LNG			
	32	31 761	LBG-32		32	33 890	LNG-32
	40	31 762	LBG-40		40	33 891	LNG-40
	50	31 763	LBG-50		50	33 892	LNG-50
	63	31 764	LBG-63		63	33 893	LNG-63
	80	31 765	LBG-80		80	33 894	LNG-80
	100	31 766	LBG-100		100	33 895	LNG-100
Clevis foot LSN				Right-angle clevis foot LQG			
	32	5 561	LSN-32		32	31 768	LQG-32
	40	5 562	LSN-40		40	31 769	LQG-40
	50	5 563	LSN-50		50	31 770	LQG-50
	63	5 564	LSN-63		63	31 771	LQG-63
	80	5 565	LSN-80		80	31 772	LQG-80
	100	5 566	LSN-100		100	31 773	LQG-100

Standard cylinders DNCB, ISO 15552

Accessories

FESTO


Ordering data – Piston rod attachments				Technical data → Internet: piston-rod attachment			
Designation	For Ø	Part No.	Type	Designation	For Ø	Part No.	Type
Rod eye SGS				Rod clevis SGA			
	32	9 261	SGS-M10x1,25		32	32 954	SGA-M10x1,25
	40	9 262	SGS-M12x1,25		40	10 767	SGA-M12x1,25
	50	9 263	SGS-M16x1,5		50	10 768	SGA-M16x1,5
	63				63		
	80	9 264	SGS-M20x1,5		80	10 769	SGA-M20x1,5
	100				100		
Rod clevis SG				Self-aligning rod coupler FK			
	32	6 144	SG-M10x1,25		32	6 140	FK-M10x1,25
	40	6 145	SG-M12x1,25		40	6 141	FK-M12x1,25
	50	6 146	SG-M16x1,5		50	6 142	FK-M16x1,5
	63				63		
	80	6 147	SG-M20x1,5		80	6 143	FK-M20x1,5
	100				100		
Coupling piece KSG							
	32	32 963	KSG-M10x1,25				
	40	32 964	KSG-M12x1,25				
	50	32 965	KSG-M16x1,5				
	63						
	80	32 966	KSG-M20x1,5				
	100						


Ordering data – One-way flow control valves				Technical data → Internet: grla	
	Connection		Material	Part No.	Type
	For Ø	For tubing OD			
	32	3	Metal design	193 142	GRLA-1/8-QS-3-D
		4		193 143	GRLA-1/8-QS-4-D
		6		193 144	GRLA-1/8-QS-6-D
		8		193 145	GRLA-1/8-QS-8-D
	40, 50	6		193 146	GRLA-1/4-QS-6-D
		8		193 147	GRLA-1/4-QS-8-D
		10		193 148	GRLA-1/4-QS-10-D
		12		193 149	GRLA-3/8-QS-6-D
	63, 80	6		193 150	GRLA-3/8-QS-8-D
		8		193 151	GRLA-3/8-QS-10-D
		10		193 152	GRLA-1/2-QS-12-D
		12			
	100				

Standard cylinders DNCB, ISO 15552

Accessories

FESTO

Ordering data – Guide units for fixed strokes (recirculating ball bearing guide only)				Technical data → Internet: feng		
	Stroke [mm]	Part No.	Type		Stroke [mm]	Part No. Type
	for Ø 32 mm				for Ø 40 mm	
	10 ... 50	34 493	FENG-32-50-KF		10 ... 50	34 499 FENG-40-50-KF
	10 ... 100	34 494	FENG-32-100-KF		10 ... 100	34 500 FENG-40-100-KF
	10 ... 160	34 495	FENG-32-160-KF		10 ... 160	34 501 FENG-40-160-KF
	10 ... 200	34 496	FENG-32-200-KF		10 ... 200	34 502 FENG-40-200-KF
	10 ... 250	150 289	FENG-32-250-KF		10 ... 250	34 503 FENG-40-250-KF
	10 ... 320	34 497	FENG-32-320-KF		10 ... 320	34 504 FENG-40-320-KF
	10 ... 400	150 290	FENG-32-400-KF		10 ... 400	150 291 FENG-40-400-KF
	10 ... 500	34 498	FENG-32-500-KF		10 ... 500	34 505 FENG-40-500-KF
	for Ø 50 mm				for Ø 63 mm	
	10 ... 50	34 506	FENG-50-50-KF		10 ... 50	34 513 FENG-63-50-KF
	10 ... 100	34 507	FENG-50-100-KF		10 ... 100	34 514 FENG-63-100-KF
	10 ... 160	34 508	FENG-50-160-KF		10 ... 160	34 515 FENG-63-160-KF
	10 ... 200	34 509	FENG-50-200-KF		10 ... 200	34 516 FENG-63-200-KF
	10 ... 250	34 510	FENG-50-250-KF		10 ... 250	34 517 FENG-63-250-KF
	10 ... 320	34 511	FENG-50-320-KF		10 ... 320	34 518 FENG-63-320-KF
	10 ... 400	150 292	FENG-50-400-KF		10 ... 400	34 519 FENG-63-400-KF
	10 ... 500	34 512	FENG-50-500-KF		10 ... 500	34 520 FENG-63-500-KF
	for Ø 80 mm				for Ø 100 mm	
	10 ... 50	34 521	FENG-80-50-KF		10 ... 50	34 529 FENG-100-50-KF
	10 ... 100	34 522	FENG-80-100-KF		10 ... 100	34 530 FENG-100-100-KF
	10 ... 160	34 523	FENG-80-160-KF		10 ... 160	34 531 FENG-100-160-KF
	10 ... 200	34 524	FENG-80-200-KF		10 ... 200	34 532 FENG-100-200-KF
	10 ... 250	34 525	FENG-80-250-KF		10 ... 250	34 533 FENG-100-250-KF
	10 ... 320	34 526	FENG-80-320-KF		10 ... 320	34 534 FENG-100-320-KF
	10 ... 400	34 527	FENG-80-400-KF		10 ... 400	34 535 FENG-100-400-KF
	10 ... 500	34 528	FENG-80-500-KF		10 ... 500	34 536 FENG-100-500-KF


Ordering data – Guide units for variable strokes				Technical data → Internet: feng	
	For Ø [mm]	Stroke [mm]	With recirculating ball bearing guide Part No. Type	With sliding bearing guide Part No. Type	
	32	10 ... 500	34 487 FENG-32-...-KF	34 481 FENG-32-...	
	40	10 ... 500	34 488 FENG-40-...-KF	34 482 FENG-40-...	
	50	10 ... 500	34 489 FENG-50-...-KF	34 483 FENG-50-...	
	63	10 ... 500	34 490 FENG-63-...-KF	34 484 FENG-63-...	
	80	10 ... 500	34 491 FENG-80-...-KF	34 485 FENG-80-...	
	100	10 ... 500	34 492 FENG-100-...-KF	34 486 FENG-100-...	

Standard cylinders DNCB, ISO 15552

Accessories

FESTO

Ordering data – Proximity sensors for T-slot, magneto-resistive					Technical data ➔ Internet: smt	
	Type of mounting	Switch output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above, flush with cylinder profile	PNP	Cable, 3-wire	2.5	543 867	SMT-8M-PS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 866	SMT-8M-PS-24V-K-0,3-M8D
			Plug M12x1, 3-pin	0.3	543 869	SMT-8M-PS-24V-K-0,3-M12
		NPN	Cable, 3-wire	2.5	543 870	SMT-8M-NS-24V-K-2,5-OE
Plug M8x1, 3-pin	0.3		543 871	SMT-8M-NS-24V-K-0,3-M8D		
	Insertable in the slot lengthwise, flush with the cylinder profile	PNP	Cable, 3-wire	2.5	175 436	SMT-8-PS-K-LED-24-B
			Plug M8x1, 3-pin	0.3	175 484	SMT-8-PS-S-LED-24-B
N/C contact						
	Insertable in the slot from above, flush with cylinder profile	PNP	Cable, 3-wire	7.5	543 873	SMT-8M-PO-24V-K7,5-OE

Ordering data – Proximity sensors for T-slot, magnetic reed					Technical data → Internet: sme	
	Type of mounting	Switch output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above, flush with cylinder profile	Contacting	Cable, 3-wire	2.5	543 862	SME-8M-DS-24V-K-2,5-OE
				5.0	543 863	SME-8M-DS-24V-K-5,0-OE
			Plug M8x1, 3-pin	2.5	543 872	SME-8M-ZS-24V-K-2,5-OE
				0.3	543 861	SME-8M-DS-24V-K-0,3-M8D
	Insertable in the slot lengthwise, flush with the cylinder profile	Contacting	Cable, 3-wire	2.5	150 855	SME-8-K-LED-24
			Plug M8x1, 3-pin	0.3	150 857	SME-8-S-LED-24
N/C contact						
	Insertable in the slot lengthwise, flush with the cylinder profile	Contacting	Cable, 3-wire	7.5	160 251	SME-8-O-K-LED-24

Ordering data – Connecting cables				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 333	NEBU-M8G3-K-2.5-LE3
			5	541 334	NEBU-M8G3-K-5-LE3
	Straight socket, M12x1, 5-pin	Cable, open end, 3-wire	2.5	541 363	NEBU-M12G5-K-2.5-LE3
			5	541 364	NEBU-M12G5-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 338	NEBU-M8W3-K-2.5-LE3
			5	541 341	NEBU-M8W3-K-5-LE3
	Angled socket, M12x1, 5-pin	Cable, open end, 3-wire	2.5	541 367	NEBU-M12W5-K-2.5-LE3
			5	541 370	NEBU-M12W5-K-5-LE3

Ordering data – Slot cover for T-slot				Part No.	Type
	Mounting	Length [m]			
	Insertable from above	2x 0.5		151 680	ABP-5-S

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com