

Installation system CPI





Installation system CPI

Key features



Key features

- Innovative
- Complete concept for decentralised machine and system structure; centralised and decentralised installation is possible in combination with the CPX terminal
- Decentralised pneumatic components and sensors for fast processes
- Centralised electric components for fieldbus and common power supply
- Flexible configuration of the individual CP strings
- Choice of valve terminal sizes for optimum pneumatic control loop systems
- Performance data as for the CP system with the addition of the comprehensive diagnostic capabilities of the CPX terminal

Sturdy

- Electrical accessories to IP65Proven valve terminals CPV (com-
- pact), MPA-S (sturdy, modular)
 Electrical input and output modules in metal housing or compact in encapsulated plastic housing
- Sturdy connection technology M12, alternatively M8
- IP20 modules for control cabinet installation with a choice of spring-loaded terminals or screw terminals

Versatile

- A number of CP interfaces can be combined under one bus node
- Four CP strings up to 10 m in length (radius) facilitate optimum decentralisation
- Max. 32 inputs and 32 outputs/ valves per string
- Available valves:
- Valve terminal CPV-SC, max.
 170 l/min flow rate
- Valve terminal MPA-S, max. 700 l/min flow rate
- Valve terminal CPV, max. 1600 l/min flow rate
- Valve terminals with I-Port interface (VTUG, CPV, MPA-L, VTUB-12, VTOC)
- Input modules with 8 ... 32 inputs and output modules with 4 ... 8 outputs, each with or without additional power supply

Operational safety

- Sturdy modules and accessories
- Ready-to-install system including CP cable (hybrid cable for data and power)
- Short circuit-proof connections with reverse polarity protection
- Valves with separate load voltage supply
- All modules equipped with local diagnostics and status LEDs
- Diagnostics of each CP string via controller/fieldbus
- Self-learning system (save button) for current configuration
- Easy replacement of modules at any time

Key features

Installation system CPI

The CPI system is capable of meeting the completely contrasting requirements created by the difference between extensive decentralised modularisation and electrical installation.

High-speed machines require short cycle times and short pneumatic tubing. The valves must be mounted close to the cylinders. The CPI system was developed to meet these requirements without having to wire each valve individually. The system integrates the modular valve terminal MPA-S with internal communication system, valve terminals with integrated sub-base CPV that are suitable for operating small pneumatic drives, and various input/output modules in a single installation concept.


All CP valve terminals and CP modules are connected using a ready-to-install CP cable, and are attached to the CP interface. 4 modules, for example one CPV valve terminal and one to three CP input modules, make up an installation string that ends at the CP interface.

Scope of services:

- Max. 4 installation strings per CP interface
- Max. 10 metre line length per string (radius)
- Max. 4 CP modules per string
- Max. 32 inputs and max. 32 outputs per string

The number of CP modules that can be connected and the number of inputs/ outputs is dependent on the type of CP module and CP interface. The maximum configuration (4 modules per string, 32 inputs/outputs) is only possible in combination with the CPX terminal and CP modules with CPI functionality.

The CP interface is the central connection point for the valve power supply and the sensor supply. The power supply for the sensors connected to the input modules is separate from the load voltage supply of the valves.




Key features

Node types Fieldbus Valve terminal VPX with CP interface CPX... CPX with CP interface CPX... CPX with CP interface CPX...

0

Peripherals overview

Integration of the installation system CPI in various connection concepts Centralised pneumatic connection (valve terminal)




Advantages

- Pneumatic multiple connector plateLess tubing required than with indi-
- vidual valves
- Common valve air supply
- Central positioning
- Material, weight and cost savings

Disadvantages

- Only effective with a large number of closely spaced actuators
- Heavier than an individual valve (lower overall weight than the same number of individual valves), which may make mounting on moving systems or in very cramped installation spaces difficult
- Longer tube lengths are occasionally required, ruling out the possibility of optimum pneumatic performance

Decentralised pneumatic connection (individual valve/valve on individual sub-base)



Advantages

- Can be positioned directly at the actuator, can even be integrated
- Short tubing length to the actuator enables short switching times
- Optimum pneumatic timing and performance possible

Disadvantages

- Air supply per valve requires more tubing
- Serial electrical links not advisable/ possible
- More complex electrical installation


Centralised electrical connection (multi-pin/fieldbus connection/standalone mini control system)

Advantages

- Internal electrical links requires less cabling
- Increased transparency
- Material, weight and cost savings
- Ideal for connecting a large number of closely spaced valves

Disadvantages


- Not suitable for individual, more widely separated applications due to the more complex cabling
- More complex individual components (cables, fieldbus modules)



Peripherals overview

Integration of the installation system CPI in various connection concepts

Decentralised electrical connection (CPI system/individual valve/valve on individual sub-base/valve manifold assembly)



Advantages

Advantages

within a system

pneumatic control chain

•

•

- CPI system with reduced installation effort for groups of actuators/ sensors
- Different levels of complexity with widely separated individual components
- Easy replacement of components during servicing
- Optimum pneumatic timing and performance possible

Scalable to different requirements

One control interface in the system,

reduces installation complexity with closely and widely spaced actuators Enables an optimum electrical and

Disadvantages

Disadvantages


ised connection

• Application must at least partially

meet the requirements of a central-

- Limited spatial expansion possible (CPI system up to 10 m, AS-Interface up to 100 m)
- High installation costs

Combined centralised and decentralised electrical connection (valve terminal with CP interface/output module)



Connecting the installation system CPI to a higher-level controller

Bus node/Industrial Ethernet

- Different bus nodes are used for integration in the control systems of various manufacturers.
- The CPI system can therefore be operated via more than 90% of the most commonly used bus systems.
- PROFIBUS
- INTERBUS
- DeviceNet
- CANopen
- CC-LINK
- EtherNet/IP
- PROFINET
- POWERLINK
- EtherCAT
- Sercos III

Control block

The optional Front End Controller CPX-


CEC permits simultaneous access via Ethernet and an integrated web server, as well as autonomous pre-processing.

- Ethernet
- TCP/IPWeb

Installation system CPI

Peripherals overview

Connecting the installation system CPI to a higher-level controller Overview



The precise technical data and specifications for CPX can be found online at:

→ Internet: cpx

Bus protocol/bus node INTERBUS	Special features
FB6	Up to 96 digital inputs/outputs6 analogue inputs/outputs
DeviceNet	
FB11	 Up to 512 digital inputs/outputs 18 analogue inputs/outputs
PROFIBUS DP	
FB13	 Up to 512 digital inputs/outputs 18 analogue inputs/outputs
CANopen	
FB14	 Up to 64 digital inputs and 64 digital outputs 8 analogue inputs and 8 analogue outputs
CC-LINK	
FB23-24	 Up to 512 digital inputs/outputs 32 analogue inputs/outputs
EtherNet/IP	
FB36	 Up to 128 digital inputs/outputs 8 analogue inputs/outputs
PROFINET	
FB33 FB34 FB35 FB43 FB44 FB45 EtherCAT	 Up to 512 digital inputs/outputs 32 analogue inputs/outputs
FB37	 Up to 512 digital inputs/outputs
ונטו	 32 analogue inputs/outputs
POWERLINK	
FB40	 Up to 512 digital inputs/outputs 32 analogue inputs/outputs
Sercos III	
FB39	 Up to 512 digital inputs/outputs 32 analogue inputs/outputs

Peripherals overview

Connecting modules in the installation system CPI CP interface within the context of the CPX terminal

Using the CP interface as a module of the CPX terminal makes it easier to progress from the CP system to the CPI system.


All CP modules are both downwards and upwards compatible and can therefore be used in the CP system and in the CPI system.

This extension has doubled the scalability and range of CP modules that can be used:

- 4 CP strings
- Up to 4 modules per string
- Up to 32 inputs and outputs per CP string

An added advantage of the CPI system is its extremely user-friendly access options via the CPX bus node and the CPX-CEC:

- Data preprocessing
- Diagnostics via software
- Reading out of status information
- Display via permanently installed or mobile unit
- Remote maintenance with CPX-CEC and Ethernet connection



Connection options

Fieldbus Direct

Special feature

The Fieldbus Direct product range is the most compact way of connecting valves to a fieldbus. The bus node is directly integrated in the electrical actuation of the valve terminal and therefore takes up only a minimal amount of space.

Fieldbus Direct and CP string extension

The optional string extension allows a further valve terminal and I/O modules to be connected to the Fieldbus Direct bus node:

- A CP string of the CP system is integrated in the bus node as an extension.
- Various input and output modules as well as valve terminals can be connected.

Application

Fieldbus Direct is a system for the compact connection of a valve terminal to different bus standards. The CP string extension option enables the functions and components of the CPI installation system to be used.

The maximum length of the CP string

extension is 10 metres, which means

mounted directly on site. All of the re-

quired electrical signals including load

current supply are transmitted via the

CP cable, which in turn means that no

further installation is needed on the

extension module.

that the extension modules can be

Characteristics of Fieldbus Direct

- Extremely compact and space-saving design
- Low-cost solution for connecting a small number of valves to the fieldbus
- Direct front-end integration with a high degree of protection IP65
- Comprehensive diagnostics and condition monitoring

The CP string interface offers:

• Max. 32 input signals

- Max. 32 output signals for output modules 24 V DC or solenoid coils
- Logic and sensor supply for the input modules

Load voltage supply for the valve terminal

of CPV valves

→ Internet: cpv

(valve terminal CPV)

Note


Detailed description of the range of


functions and combination options

• Logic supply for the output module

Connection options

Fieldbus Direct with CP string extension CPV valve terminal






- 4 to 8 valve positions
- DeviceNet

• 4 to 16 solenoid coils

More information → Internet: cpv

Compact vision system SBOC-Q/SBOI-Q with CP interface



The compact vision system SBOx-Q can be integrated into a Festo CPI network. In this case it functions like a binary module with 16 inputs and 16 outputs.

- Address requirement: 16 digital inputs/outputs
- CPI connection
- More information
- → Internet: sboc-q, sboi-q

Installation system CPI

Connection options

Connecting inputs and outputs in the i	installation system CDI		
CP connecting cable	installation system CF1		
STATE OF THE ST	 KVI-CP-3 -	 Pre-assembled cables for connecting the CP modules Lengths from 0.25 to 8 metres M9 plug/socket, 5-pin Straight/angled version in any combination 	More information → Internet: kvi-cp
CP input/output modules in sturdy, univ	versal and compact design or as valve term	inal	
Input and output modules with differ- ent electrical interfaces are available for connecting sensors and actuators:	 M12-5POL M8-3POL M8-4POL Spring-loaded terminal or screw terminal technology 	The maximum number of inputs/out- puts that can be connected to the indi- vidual modules can vary depending on the application. The following module sizes are available:	 Input modules with 8, 16 or 32 channels Output modules with 4 or 8 channels CPV with 4, 6 or 8 valve slices (max. 16 valves) MPA-S with 2 32 valves
Valve terminals with CP interface			
	CPV10 CPV14 CPV18	 Max. 16 valves in 8 valve slices Highly compact and space-saving Width 10, 14, 18 mm Nominal flow rate 400/800/1600 l/min CPV10 and CPV14 with CPI functionality CPV18 with CP functionality 	More information → Internet: cpv (valve terminal CPV)
Valve terminal MPA-S			
	MPA1 MPA14 MPA2	 Max. 32 valves (32 solenoid coils, 16 valve positions) Modular and versatile Width 10, 14, 20 mm Nominal flow rate 360/550/700 l/min CPI functionality 	More information → Internet: mpa-s (valve terminal MPA-S)
Valve terminal MPA-S			
	CPV-SC	 Max. 16 valves Extremely compact Width 10 mm Nominal flow rate 170 l/min CPI functionality 	More information → Internet: cpv-sc (valve terminal CPV-SC)
Valve terminal with I-Port interface			_
	Valve terminals: • VTOC • VTUB-12 • CPV • MPA-L • VTUG	Flow rate • 10 l/min • 400 l/min • 400/800 l/min • 360/670/700 l/min • 130 1200 l/min	More information → Internet: vtoc → Internet: vtub-12 → Internet: cpv → Internet: mpal → Internet: vtug → Internet: cteu

Key features – Input/output modules

Connecting inputs and outputs in the Special features of the CP I/O modules i			
The sturdy CP I/O modules have a highly resistant aluminium housing and their internal electronic compo- nents can be repaired or replaced.	CP-EZ or output modules have a sep- arate load voltage supply, which means less load on the CP interface and CP cable and more power for the connected consum- ing devices.	This also makes it easier to disconnect the consuming devices separately.	High degree of protection IP65, sur- passed only by the compact CP mod- ules with IP65/67 protection. The only exception is the IP20 protection of- fered by the module with clamped ter- minal connection for installation in control cabinets.
CP input modules in sturdy design			
	CP-E16-M12x2-5POL	 16 inputs 24 V DC Signal status indication via 16 LEDs Operating status indication CP functionality 	 M12 plug, double allocation 1x M9 CP connection PNP/NPN, IP65
	CP-E16-M8	 16 inputs 24 V DC Signal status indication via 16 LEDs Operating status indication CP functionality 	 M8 plug, single allocation 1x M9 CP connection PNP/NPN, IP65
	CP-E16-M8-Z	 16 inputs 24 V DC Signal status indication via 16 LEDs Operating status indication CP functionality 	 Galvanic isolation through additional power supply M8 plug, single allocation 1x M9 CP connection Separate sensor supply PNP/NPN, IP65
CP output modules in a sturdy design			
	CP-A08-M12-5POL	 8 outputs 24 V DC Output signal display via 8 LEDs Operating status indication M12 plug, single allocation CP functionality 	 2x M9 CP connection Separate load voltage Outputs resistant to overloads and short circuits PNP, IP65

Key features - Input/output modules

Connecting inputs and outputs in the installation system CPI

Special features of the CP I/O modules in economical design

In addition to the sturdy CP I/O modules and the compact CP I/O modules, there are also the economical modules with the design features of the compact modules, but with a greater number of inputs/outputs. The economical CP modules feature a compact design, coupled with a large number of inputs/outputs.

The modules can be used in combination with the following valve terminals: • CPV, MPA-S, CPV-SC

- Application:
- Same function, configuration and commissioning as sturdy or compact CP modules
- Integrated H-rail mounting and earthing plate
- Centrally placed status and diagnostic LEDs
- The economical CP modules and the other CP modules can be operated together on a string
- The maximum number of modules per CP string is as follows:
 - CPI system: max. 4 modules or max. 32 inputs and 32 outputs
 - CP system: one valve terminal/ output module and one input module

CP input modules in economical design



• PNP, IP65

Key features – Input/output modules


Connecting inputs and outputs in the installation system CPI Special features of the CP I/O modules in compact design

Special features of the CP I/O modules in	n compact design		
In addition to the sturdy and economi- cal CP input/output modules, there is also the compact series of CP I/O mod- ules. These have an optimised, space-saving design, are made from plastic and are very light. They are, of course, available with the high degree of protection IP65/67 (exception: clamping modules to IP20 for installa- tion in protected installation spaces).	 The compact CP modules are designed for use in handling and assembly wherever space requirements and product weight play a role. The modules can be used in combina- tion with the following valve terminals: CPV, MPA-S, CPV-SC 	 Application: The modules can be positioned even closer to the actuators thanks to the smaller dimensions. Same function, configuration and commissioning as sturdy or econom- ical CP modules The compact CP modules and the other CP modules can be operated together on a string 	 The maximum number of modules per CP string is as follows: CPI system: max. 4 modules or max. 32 inputs and 32 outputs CP system: one valve terminal/ output module and one input module
CP input modules in compact design			
	CP-E08-M12x2-CL	 8 inputs 24 V DC Signal status indication via 8 LEDs Operating status indication CPI functionality 	 4x M12 plug, 5-pin, double allocation 2x M9 CP connection PNP, IP65/67
	CP-E08-M8-CL	 8 inputs 24 V DC Signal status indication via 8 LEDs Operating status indication CPI functionality 	 8x M8 plug, 3-pin, single allocation 2x M9 CP connection PNP, IP65/67
A REAL PROPERTY OF THE PARTY OF	CP-E16-KL-CL	 16 inputs 24 V DC Indirect signal status indication via LEDs in the connection set of the tension-spring socket Operating status indication CPI functionality 	 Screw terminal or tension-spring sockets 2x M9 CP connection PNP, IP20
CP output modules in compact design			
	CP-A04-M12x2-CL	 4 outputs 24 V DC Signal status indication via 4 LEDs Operating status indication CPI functionality 	 4x M12 plug, 5-pin, double allocation 2x M9 CP connection Outputs resistant to overloads and short circuits PNP, IP65/67

Key features - Mounting options

H-rail mounting

CP interface




The H-rail mounting is part of the rear profile of the CPX interlinking blocks. The CPX terminal can be attached to the H-rail using the H-rail mounting kit. The CPX terminal is first hooked onto the H-rail (see arrow 1), then swivelled onto the H-rail and secured in place with the clamping ele-

ment (see arrow 2).

The following mounting kit is required for H-rail mounting (plus mounting kit for optionally mounted valves):CPX-CPA-BG-NRH

This enables mounting on H-rails to EN 60715.


Economical CP modules



The H-rail mounting is impressed in the reverse profile of the economical CP modules. The modules can be attached to the H-rail using the H-rail mounting. The module is first hooked onto the H-rail (see arrow 1), then swivelled onto the H-rail and secured in place with the clamping element (see arrow 2). The scope of delivery includes the following mounting kit for H-rail mounting:CP-EL-HSThis enables mounting on H rails t

This enables mounting on H-rails to EN 60715.

Compact and sturdy CP modules




For the CP modules there is a mounting kit that can be used on an H-rail. On the compact CP modules, the mounting holes are covered by inscription labels. The following mounting kit is needed for H-rail mounting:


• CP-TS-HS35

This enables mounting on H-rails to EN 60715.


Key features – Mounting options


Wall mounting CP modules





The CP modules (with screws up to 4 mm in diameter) can be mounted on even surfaces in almost any position using the mounting holes.





🛔 - Note


The mounting holes on the compact CP modules are covered by inscription labels.

Key features - Inscription system

Inscription system

All CP modules have holders for inscription labels.


Sturdy CP modules



Inscription labels/label holders are not included in the scope of delivery and can be ordered separately. The labels can be pre-assembled on request.


The sturdy CP modules have two slots in which the inscription labels IBS-6x10 (part no. 18576) can be fitted. At least one inscription label can be fitted per connection. The IBS-6x10 are plastic clips that can be printed on, written on or affixed with labels.

Economical CP modules



The economical CP modules have six fixtures on the side, each for one inscription label holder ASCF-H-E2 (part no. 547473). The ASCF-H-E2 are transparent, hinged inscription label holders for holding premade paper inscription labels. The label can be read when the label holder is opened out.

Compact CP modules



The compact CP modules have a holder for an inscription label IBS-8x20 (part o. 539388) for each connection. The IBS-8x20 are plastic clips that can be printed on, written on or affixed with labels.

Key features – Power supply

Operating voltage and load current supply

The following functions are made available to the connected modules through the CP cable:

- Connection for data exchange
- Operating voltage for the internal electronics
- Load current supply for the connected inputs/sensors and/or outputs/ actuators

Example of circuits for additional power supply

CP-E...Z or output modules from the sturdy and the economical series have a separate load voltage supply:


- Less load on the CP interface and CP cable
- 0.5 A per output (max. 4 A supply per output module)
- 1 A per 8 inputs
- · Separate disconnection of the consuming devices possible

Every module in the CPI system is protected separately against overload with electronic fuses. The input modules without additional supply provide a maximum sensor supply of 500 mA in the sturdy design,

800 mA in the compact design and 700 mA in the economical design with 16 inputs and 1400 mA with 32 inputs.

The input modules with additional supply provide up to 2 A aggregate current for the connected sensors.

- [1] Load voltage supply (can be disconnected separately)
- [2] External fuses
- [3] PE
- [4] Equipotential bonding
- Earth connection pin 4, designed [5] for 12 A




Pin allocation of plug for additional power supply

Pin allocation of plug for additional power supply						
Pin allocation	Pin	Signal	Designation			
2 3	1	24 V DC	Supply for electronics and inputs			
	2	24 V DC	Load supply for valves/outputs			
	3	0 V	Equipotential bonding			
	4	0 V	Earth terminal and equipotential bonding, rated for 12 A			
4						

Key features – Power supply

Power supply concept of the CPX terminal

Circuit diagram for M18 power supply/system supply (example)



Interlinking blocks

Many applications require the voltage to be segmented into zones. This applies in particular to the separate disconnection of connected actuators (solenoid coils/outputs). The separation of voltages for valves and the creation of different voltage segments for electrical outputs and sensors are supported by the different interlinking blocks of the CPX terminal:

- With system supplyWithout power supply
- With additional power for electrical outputs
- With additional supply for valves

The use of decentralised devices on the fieldbus – particularly with a high degree of protection for direct machine mounting – demands a flexible power supply concept. The CPX terminal makes it easier to connect all voltages via one socket.

[≜] - Note

The CP interface connects the 0 V of the power supply for the electronics/inputs and the valves.

The supply voltages are supplied using

а

• 4-pin M18 plug

• 4-pin 7/8" plug

• 5-pin 7/8" plug

• AIDA push-pull, 5-pin

A distinction is made between supply for

- electronics and sensors/inputs
- valves
- actuators/outputs

Selectable connection technology:

- M18
- 7/8"
- AIDA push-pull

To prevent overloads, the power must therefore be supplied using just one power supply module or using power supply units with a common PEN conductor.

- Note

The max. current is limited to 12 A with the 7/8" system supply. When using a conventional pre-assembled cable, the max. current is limited to 8 A.

Key features – Diagnostics

General limits System supply

The system supply provides the internal voltage for the entire CPX system with

- max. 16 A for electronics and sensors/inputs
- max. 16 A for actuators/outputs and valves

Diagnostics General

A comprehensive diagnostic function is

available for each string. The diagnostic information can either be detected via the LEDs on the module and then read out and evaluated via the controller software (non-fieldbus-specific) or displayed directly on the CPX terminal via the diagnostic interface and then evaluated and processed.

Diagnostics via CPX terminal

CP interface


The CP interface and the CP modules connected to the CP interface get their operating voltage from the connection for electronics and sensors/inputs. The operating voltage for the sensors/ actuators connected to the CP modules is supplied from the voltage for valves. The CP interface supplies the connected CP modules with • max. 1.6 A per CP string

- Diagnostics via LEDs
- Error in bus communication
- POWER, power supply indicator for internal electronics
- POWER V, load voltage indicator for valves
- 0 ... 3, CP string allocation changed or interrupted

There are also bus-specific LED displays.

Diagnostics via control program

- Configuration error
- Bus error
- Operating voltage failure
- Falling below voltage tolerance (valves)
- Short circuit in sensor voltage supply
- Operating voltage failure at the output modules
- Short circuit/overload at the output modules
- Connection to one or more CP modules interrupted (valve terminal, input/output modules)




6

- [1] Diagnostics via controller/bus node
- [2] Bus-specific LEDs
- [3] String diagnostics via LED on the CP interface
- [4] Diagnostics via CP string
- [5] Diagnostics via LED on CP module
- [6] Status indicator on the CP module


Key features - CP interface

Diagnostics

Diagnostics via CP bus node



Diagnostic LEDs on the CP modules



Parameterisation

The addresses to the individual actuators/outputs or sensors/inputs, which are connected to the CP modules, are allocated in accordance with the bus node or CPX-CEC used (exception: INTERBUS node).

Address allocation is performed in accordance with the following rules:

- One CP interface provides four strings with a total of 128 input and 128 output addresses.
- A used string occupies 32 input and 32 output addresses.
- The addresses are permanently allocated to the strings and CP modules in ascending order.
- Unused address space remains reserved for future extensions.

The CP interface checks the configuration of the connected modules each time the system is switched on and during operation. If a deviation from the saved configuration is detected, an appropriate message is output via the controller software and displayed via LED.

[1] Status LED

(red)

(PS, green)

dication, green)

CP communication

[2] Status LED (module) for short cir-

[3] Status LEDs for inputs (status in-

CP-E16-...-EL) for short circuit/

overload of sensor supply (red)

[4] Status LED (group, only with

cuit/overload of sensor supply

The configuration detected is stored by pressing the Save button (after the operating voltage is switched on at the CP interface).

[1] Diagnostics via fieldbus

- [2] Bus-specific LEDs
- [3] String diagnostics via LED on the bus node
- [4] Diagnostics via LED on CP module
- [5] Diagnostics via CP string
- [6] Status indicator on the CP module

In addition to the status indication per module and per individual channel/ input, the economical modules with 16 inputs additionally have a status indication for a group of four inputs. The following inputs are combined into groups of four:

- 0...3
- 4...7
- 8...11
- 12...15

The configuration is stored each time the CP interface is switched off and back on.

There is an option to replace a connected CP module with an identical module during operation. Removal of more than one module from the current configuration will be detected as an error; the address spaces of these modules will no longer be actuated.

Installation system CPI

Selection aid


System selection aid					
	Modules per string	Outputs/inputs per string	Modules with CP functionality	Modules with CPI functionality	String length [m]
CP system	2	16/16	0 1 input module	0 1 input module	0 10
			0 1 output module	0 1 output module	
CPI system	4	32/32	0 1 input module	0 4 input modules	010
			0 1 output module	0 4 output modules	

	Functionality	,	Additional power	Additional power Address requirement		Max. current consumption	→ Page/Internet
	СР	CPI	supply	Inputs	Outputs	[A]	
Input modules							
CP-E16-M8	•	-	-	16	-	0.54	26
CP-E16-M12x2-5POL	•	-	-	16	-	0.59	26
CP-E16-M8-Z	•	-	•	16	-	1.04	27
CP-E16-M8-EL	•	•	-	16	-	0.7	32
CP-E16-M12-EL	•	•	-	16	-	0.7	32
CP-E08-M12-CL	•	•	-	8	-	0.835	37
CP-E08-M8-CL	•	•	-	8	-	0.835	37
CP-E16-KL-CL			-	16	-	0.835	37
Output modules						_	
CP-A08-M12-5POL	•	-		-	8	2.09	43
CP-A08-M12-EL-Z	•	•	•	-	8	4	46
CP-A04-M12-CL			-	-	4	1.035	50
Connecting cables							
KVI-CP-3			-	-	-	1.6	kvi-cp
Valve terminals							
CPV10-FB-4	•		-	-	16	0.327	срv
CPV10-FB-6	•	•	-	-	16	0.465	сру
CPV10-FB-8	•		-	-	16	0.604	сру
CPV14-FB-4	•	•	-	-	16	0.419	сру
CPV14-FB-6	•	•	-	-	16	0.603	сру
CPV14-FB-8	•	•	-	-	16	0.788	сру
CPV18-FB-4	•	-	-	-	16	0.624	сру
CPV18-FB-6	•	-	-	-	16	0.911	сру
CPV18-FB-8	•	-	-	-	16	1.197	сру
MPA-S	-	•	•	-	32	3.25	mpa-s
CPV-SC	-	•	-	-	16	0.875	cpv-sc
CTEU-CP	-		-	0/16/32	0/16/32	3.4	54

Selection aid

Accessory selection aid

Connection M8, 3-pin



NEBU-...-M8G3


M8 socket, 3-pin M8 socket, 4-pin M12 socket, 5-pin Open cable end

- 闄 - Note

Festo delivers pre-assembled M8/ M12 connecting cables (NEBU modular system) on request:

- Tailored to the application
- Perfectly fitting
- Easy to install

Selection aid




[1] Input modules	[2] Plugs		[1] Input modules	[2] Plugs	
Туре	Туре	Connection technology	Туре	Туре	Connection technology
CP-E16-M12x2-5POL	SEA-M12-5GS-PG7	Screw terminal	CP-E16-KL-CL	PS1-SAC31-30POL+	ED Screw-in tension-spring
CP-E16N-M12-EL	SEA-5GS-11-DUO	Screw terminal			socket
CP-E08-M12-CL					

Installation system CPI

Selection aid

Accessory selection aid

Connection for outputs M12, 5-pin



Datasheet - Input modules CP-E16

Function

Digital input modules make it easier to connect proximity switches or other 24 V DC sensors (inductive, capacitive, etc.).

M12 plugs with double allocation are separated using a sensor/actuator distributor.

Area of application

- Input modules for 24 V DC sensor signals
- M8 and M12 plugs, single allocation with 16 connections, double allocation with 8 connections
- M12 plug, 5-pin
- The input statuses for each input signal are indicated via an assigned LED.
- 24 V DC supply provided for all connected sensors
- Diagnostic LED for short circuit/undervoltage of sensor supply.
- Diagnostic LED for short circuit/interruption of external sensor supply with CP-E-16-M8-Z.



General technical data

lyp)(

Туре			CP-E16-M8	CP-E16-M12x2-5POL
			Positive switching	Positive switching
Number of inputs			16	
Allocation of inputs			Single allocation	Double allocation
Sensor connection type			16x M8, 3-pin	8x M12, 5-pin
Power supply 24 V DC			Coming from the bus node	
Intrinsic current consumption o	felectronics	[mA]	40	90
Input current at 24 V DC (from s	iensor)	[mA]	Typically 8	Typically 6
Fuse protection for sensors and	l electronics modules		Internal electronic short circuit p	rotection
Max. current consumption of se	Max. current consumption of sensor supply, aggregate current [A]			
Sensor supply voltage		[V DC]	24 ±25%	
Reverse-polarity protection			For logic and sensor voltage	
Galvanic isolation			None	
Switching level	Signal 0	[V]	≤5	≤6
	Signal 1	[V]	≥11	≥8.6
Input delay		[ms]	Typically 5	Typically 3
Switching logic			PNP	PNP
Input characteristic			To IEC 1131-2	
Connection to bus node			Via pre-assembled cables	
Degree of protection to EN 6052	29		IP65 (when fully plugged in or fitted with protective cover)	
Temperature range	Operation	[°C]	-5 +50	
	Storage	[°C]	-20 +70	
Material			Die-cast aluminium	
PWIS conformity			VDMA24364-B2-L	
Dimensions		[mm]	148.9 x 66 x 47.9	140.9 x 78 x 55.2
Weight		[g]	400	500

1

Datasheet – Input modules CP-E16

General technical data					
Туре			CP-E16-M8-Z		
			Positive and negative switching	ng	
Number of inputs			16		
Allocation of inputs			Single allocation		
Sensor connection type			16x M8, 3-pin		
Power supply 24 V DC			Coming from the bus node, co	onnection for additional sensor supply	
Intrinsic current consumption of		[mA]	40		
Input current at 24 V DC (from s	sensor)	[mA]	Typically 8		
Fuse protection for sensors and	l electronics modules		Electronic short circuit protect	tion per group	
Max. current consumption of se	ensor supply, aggregate current	[A]	Max. 1 per group of 8 inputs		
Sensor supply voltage		[V DC]	24 ±25%		
Reverse-polarity protection			For logic and sensor voltage		
Galvanic isolation			None		
Switching level			PNP	NPN	
	Signal 0	[V]	≤6	≥-8.6	
	Signal 1	[V]	≥8.6	≤-6	
Input delay		[ms]	Typically 3		
Switching logic			PNP/NPN		
Input characteristic			To IEC 1131-2		
Connection to bus node			Via pre-assembled cables		
Degree of protection to EN 605	29		IP65 (when fully plugged in or fitted with protective cover)		
Temperature range	Operation	[°C]	-5+50		
	Storage	[°C]	-20 +70		
Material		Die-cast aluminium			
PWIS conformity		VDMA24364-B2-L			
Dimensions		[mm]	216.9 x 66 x 50.6		
Weight		[g]	420		

Certifications


certifications	
Туре	CP-E16-M
ATEX category for gas	II 3G
Type of ignition protection for gas	Ex nA IIC T5 X Gc
ATEX category for dust	II 3D
Type of ignition protection for dust	Ex tc IIIC T80°C X Dc IP65
ATEX ambient temperature [°C]	-5 ≤ Ta ≤ +50
CE marking (see declaration of conformity)	To EU EMC Directive ¹⁾
	To EU Explosion Protection Directive (ATEX)
KC mark	KC EMC
Certification	c UL us - Recognized (OL)
	C-Tick

1) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... -> Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Datasheet – Input modules CP-E16





- [1] CP connection
- [2] Slot for identification labels (IBS-6x10)
- [3] Identification of input type: -INPUT-P for PNP inputs
- [4] Status LED (green)
- [5] Sensor connections
- [6] Green LED for status indication (one LED per input)


Pin allocation for sensor connections CP-E16-M12x2-5Pol
PIN allocation for sensor connections CP-E16-M12X2-5Pol


Pin allocation	Pin	Signal	Designation	Pin	Signal
\frown	1	24 V	Operating voltage 24 V	1	24 V
1 Ex+2 3	2	lx+1*	Sensor signal	2	lx+3*
	3	0 V	Operating voltage 0 V	3	0 V
	4	lx*	Sensor signal	4	lx+2*
44 2 2 4 Ex+1 3 Ex+3 1	5	Ground	Earth terminal	5	Ground

lx = Input x

Datasheet – Input modules CP-E16

Connection and display components CP-E16-M8-Z





- [3] Slot for identification labels
- (IBS-6x10)[4] Connection for the power supply to the external sensors
- [5] Red LED for indicating short circuit or failure of the sensor voltage (one LED per input group)
- [6] Sensor connections
- [7] Green LED for status indication (one LED per input)

P-E16-M8- Pin	Signal	Designation	
1	24 V DC ±25% PNP/NPN	Operating voltage Coding with negative/positive switching: • PNP operation (nin 2 and 3 bridged)	- 闄 - Note External sensor supply for CP-E16-M8-Z:
3	NPN operation (pin 2 at OPerating voltage 0 V	NPN operation (pin 2 and 1 bridged) Operating voltage 0 V	Specified for PNP or NPN operation (type CP-E16-M8-Z). The input module provides PNP or NPN inputs. You can determine either PNP or
5	Ground	Earth terminal	NPN operation by installing a bridge in the socket of the sensor supply connection.
	Pin 1 2 3 4 5	1 24 V DC ±25% 2 PNP/NPN 3 0 V 4 n.c.	Pin Signal Designation 1 24 V DC ±25% Operating voltage 2 PNP/NPN Coding with negative/positive switching: PNP operation (pin 2 and 3 bridged) NPN operation (pin 2 and 1 bridged) 3 0 V Operating voltage 0 V 4 n.c. Not connected Not connected


Pin allocation – Sensor connections CP-E16-M8-Z

Pin allocation	Pin	Signal	Designation	Pin	Signal
	1	24 V	Operating voltage 24 V	1	24 V
	3	0 V	Operating voltage 0 V	3	0 V
	4	lx*	Sensor signal	4	Ix+1*

* Ix = Input x

Datasheet - Input modules CP-E16

Connection and display components CP-E16-M8



[1] CP connection

- [2] Slot for identification labels (IBS-6x10)
- [3] Status LED (green)
- [4] Sensor connections
- [5] Green LED for status indication (one LED per input)

Pin allocation – Sensor connections CP-E16-M8

Pin allocation – Sensor connections CP-E16-M8							
Pin allocation	Pin	Signal	Designation	Pin	Signal		
	1	24 V	Operating voltage 24 V	1	24 V		
	3	0 V	Operating voltage 0 V	3	0 V		
	4	lx*	Sensor signal	4	lx+1*		

* lx = Input x

Accessories – Input modules CP-E16

Ordering data						1
esignation					Part no.	Туре
nput modules						
Ś	Positive switching				18205	CP-E16-M8
	Positive switching				175561	CP-E16-M12x2-5POL
	Positive and negative switch	ing	189670	CP-E16-M8-Z		
ower supply						
A CONTRACTOR	Power supply socket, straigh	t, M12x1, 5-pin			18324	FBSD-GD-9-5POL
ensor plug						
	Plug, straight socket, M12x1		5-pin	PG7	175487	SEA-M12-5GS-PG7
			4-pin	PG7	18666	SEA-GS-7
			4-pin	2.5 mm ² 0.D.	192008	SEA-4GS-7-2.5
	Plug, straight, M8x1		3-pin	Solderable	18696	SEA-GS-M8
				Screw-in	192009	SEA-3GS-M8-S
	Plug for 2 connecting cables,	M12x1, PG11	4-pin		18779	SEA-GS-11-DUO
			5-pin		192010	SEA-5GS-11-DUO
Connecting cables						
\bigcirc	Connecting cable M8-M8	3-pin	Straight plug/	0.5 m	541346	NEBU-M8G3-K-0.5-M8G3
200			straight socket	1.0 m	541347	NEBU-M8G3-K-1-M8G3
C. M. C.				2.5 m	541348	NEBU-M8G3-K-2.5-M8G3
A LAND AND A LAND				5.0 m	541349	NEBU-M8G3-K-5-M8G3
	Modular system for a choice	of connecting cables	·	•	-	NEBU
						→ Internet: nebu
Nounting						,
A CONTRACTOR	Mounting for H-rail				170169	CP-TS-HS35

Datasheet – Input modules CP-E...-EL

Function

Digital input modules make it easier to connect proximity switches or other 24 V DC sensors (inductive, capacitive, etc.).

Plugs with double allocation are separated using a sensor/actuator distributor.

Area of application

- Input modules for 24 V DC sensor signals
- M8 and M12 connection technology
- Display of the input statuses for each input signal via an assigned LED
- Operating voltage supply 24 V DC for all connected sensors
- Diagnostic LED for short circuit/overload of sensor supply
- Circumferential labelling with large, hinged inscription label
- Earthing plate and H-rail mounting already integrated



General technical data

Туре			CP-E16-M12-EL	CP-E16-M8-EL		
			Positive switching	Positive switching		
Number of inputs			16			
Allocation of inputs			Double allocation	Single allocation		
Sensor connection type			8x M12, 5-pin	16x M8, 3-pin		
Power supply 24 V DC			Via CP connection			
Intrinsic current consumption	at operating voltage	[mA]	Typically 75			
Fuse protection (short circuit)			Internal electronic fuse protection	on for each group		
Max. aggregate current per m	odule	[A]	0.7			
Nominal operating voltage			24			
Operating voltage range		[V DC]	18 30			
Residual ripple load voltage		[Vss]	4			
Electrical isolation between c	hannels		None			
Switching level	Signal 0	[V]	≤ 6			
	Signal 1	[V]	≥ 8.6			
Debounce time at inputs		[ms]	3 (0.5 ms, 10 ms, 20 ms parame	eterisable)		
Switching logic			PNP			
Input characteristic			To IEC 1131-T2			
Connection to bus node			Via pre-assembled cables			
Diagnostics			CP communication			
			Short circuit/overload			
			Undervoltage			
LED displays			2 module diagnostics	2 module diagnostics		
			16 channel status	16 channel status		
			4 group diagnostics	4 group diagnostics		

Datasheet – Input modules CP-E...-EL

Materials

Housing	Reinforced PA
Cover	Reinforced PA
Note on materials	RoHS-compliant
PWIS conformity	VDMA24364-B2-L

Operating and environmental conditions

Degree of protection to EN 60529		IP65/IP67 (when fully plugged in or fitted with protective cap)
Ambient temperature	[°C]	-5 +50
Storage temperature	[°C]	-20+70
Corrosion resistance class CRC ¹⁾		1
CE marking (see declaration of conformity)		To EU EMC Directive ²⁾
		To EU RoHS Directive ²⁾
UKCA marking (see declaration of conformity)		To UK instructions for EMC ²⁾
		To UK RoHS instructions ²⁾
KC mark		KC EMC
Certification		c UL us listed (OL)
		RCM mark
		C-Tick

1) More information: www.festo.com/x/topic/kbk


2) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Datasheet – Input modules CP-E...-EL


Connection and display components

CP-E16-M12-EL



- [1] CP connection, outgoing
- [2] CP connection, incoming
- [3] Status LED (module) for short circuit/overload of sensor supply (red)
- [4] Status LED for CP communication (green)
- [5] Status LEDs for inputs (status indication, green)
- [6] Status LED (group) for short circuit/overload of sensor supply (red)
- [7] Fixture for inscription label holder ASCF-H-E2
- [8] Sensor connections (2 inputs per socket)


Pin allocation for sensor connections CP-E16-M12-EL Pin allocation




* Ix = Input x


Datasheet - Input modules CP-E...-EL





- CP connection, outgoing
 - CP connection, incoming
- Status LED (module) for short circuit/overload of sensor supply
- [4] Status LED for CP communication
- Status LEDs for inputs (status indication, green)
- [6] Status LED (group) for short circuit/overload of sensor supply (red)
- [7] Fixture for inscription label holder ASCF-H-E2
- [8] Sensor connections (1 input per socket)





lx = Input x

Accessories – Input modules CP-E...-EL

Ordering data								
Designation					Part no.	Туре		
Input modules								
	Positive switching				546923	CP-E16-M12-EL		
	Positive switching				546922	CP-E16-M8-EL		
Plug								
~	Plug, straight socket, M12x1		5-pin	PG7	175487	SEA-M12-5GS-PG7		
			4-pin	PG7	18666	SEA-GS-7		
			4-pin	2.5 mm ² 0.D.	192008	SEA-4GS-7-2.5		
~	Plug, straight, M8x1		3-pin	Solderable	18696	SEA-GS-M8		
				Screw-in	192009	SEA-3GS-M8-S		
	Plug for 2 connecting cables,	M12x1, PG11	4-pin		18779	SEA-GS-11-DUO		
			5-pin		192010	SEA-5GS-11-DUO		
Distributors								
STREET, STREET	Modular system for all types	of sensor/actuator distribu		-	NEDY → Internet: nedy			
	Push-in T-connector	1x plug M8, 4-pin	2x socket M8, 3-	pin	8005312	NEDY-L2R1-V1-M8G3-N-M8G4		
		1x plug M12, 4-pin	2x socket M8, 3-	pin	8005311	NEDY-L2R1-V1-M8G3-N-M12G4		
			2x socket M12, 5	2x socket M12, 5-pin		NEDY-L2R1-V1-M12G5-N-M12G4		
Inscription label holders								
	Inscription label holders for EL modules, bag of 10 547473 ASCF-H-E2							
User documentation								
	User documentation for inpu	t/output modules	German	539299	P.BECPEA-CL-DE			
				English	539300	P.BECPEA-CL-EN		
				French	539302	P.BECPEA-CL-FR		
				Italian	539303	P.BECPEA-CL-IT		
				Spanish	539301	P.BECPEA-CL-ES		
	1							

Function

Digital input modules make it easier to connect proximity switches or other 24 V DC sensors (inductive, capacitive, etc.).

Plugs with double allocation are separated using a sensor/actuator distributor.

Area of application

- Input modules for 24 V DC sensor signals
- M8 and M12 plug connection technology
- M12 input module, inputs with double allocation. M8 inputs with single allocation
- M12 plug, 5-pin
- The input statuses for each input signal are indicated via an assigned LED.
- 24 V DC supply provided for all connected sensors
- Diagnostic LED for short circuit/ undervoltage of sensor supply.
- Modules support the CPI functionality (only in combination with the CPX CP interface)



General technical data

Туре			CP-E08-M12-CL Positive switching	CP-E08-M8-CL Positive switching	CP-E16-KL-CL Positive switching	
Number of inputs			8		16	
Allocation of inputs			Double allocation	Single allocation		
Sensor connection type			4x M12, 5-pin	8x M8, 3-pin	Spring-loaded terminals or screw terminals	
Power supply 24 V DC			From the bus node, basi	c unit, CP interface, etc.		
Intrinsic current consumption	n of electronics	[mA]	Typically 35 (inputs not o	connected)		
Input current at 24 V DC (from	n sensor)	[mA]	Typically 6			
Fuse protection for sensors a	nd electronics modules		Internal electronic short	Internal electronic short circuit protection		
Max. current consumption fo	r sensor supply, aggregate current	[A]	Max. 0.8			
Nominal operating voltage fo	r sensors		24			
Operating voltage range for s	ensors	[V DC]	18 30			
Reverse-polarity protection			For logic and sensor supply			
Galvanic isolation			None			
Switching level	Signal 0	[V]	≤5			
	Signal 1	[V]	≥-11			
Input delay		[ms]	Typically 3			
Switching logic			PNP			
Input characteristic			To IEC 1131-2			
Connection to bus node			Via pre-assembled cable	es		
Diagnostics			Undervoltage			
			Short circuit/overload in	sensor supply		

General technical data				
Туре		CP-E08-M12-CL	CP-E08-M8-CL	CP-E16-KL-CL
		Positive switching	Positive switching	Positive switching
PWIS conformity		VDMA24364-B2-L		
Dimensions (WxLxH)	[mm]	151 x 30 x 25		
Weight	[g]	165	190	145

Operating and environmental conditions

operating and environmental conditions			
Туре	CP-E08-M12-CL	CP-E08-M8-CL	CP-E16-KL-CL
Degree of protection to EN 60529	IP65/IP67 (when fully plugged	d in or fitted with protective	IP20
	cap)		
Ambient temperature [°C]	-5 +50		
Storage temperature [°C]	-20 +70		
Corrosion resistance class CRC ¹⁾	1		
CE marking (see declaration of conformity)	To EU EMC Directive ²⁾		
	To EU RoHS Directive		
	To EU Explosion Protection Di	rective (ATEX)	-
UKCA marking (see declaration of conformity)	To UK instructions for EMC		
	To UK RoHS instructions		
	To UK EX instructions		-
KC mark	KC EMC		
Certification	c UL us listed (OL)		
	RCM		

1) More information: www.festo.com/x/topic/kbk

2) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... → Support/Downloads.


If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

ATEX certifications			
Туре	CP-E08-M12-CL	CP-E08-M8-CL	CP-E16-KL-CL
ATEX category for gas	II 3G		-
Type of ignition protection for gas	Ex ec IIC T6 Gc X		-
ATEX category for dust	II 3D		-
Type of ignition protection for dust	Ex tc IIIC T70°C IP67 Dc X		-
ATEX ambient temperature [°C]	-5 ≤ Ta ≤ +50		-
Explosion protection certification outside the EU	EPL Dc (GB)		-
	EPL Gc (GB)		-

- 闄 - Note

When operating device combinations in potentially explosive areas, the lowest common zone, temperature class and ambient temperature of the individual devices determine the possible use of the entire module. I






[1] (CP	connection,	incoming
-------	----	-------------	----------

- [2] Status LED (green)
- [3] Green LED for status indication (one LED per input)
- [4] Holder for inscription label (IBS-8x20)
- [5] Red LED for short circuit/overload display
- [6] CP connection, outgoing
- [7] Sensor connections


Pin allocation for sensor connections CP-E08-	Pin	Signal	Designation
	FIII	Siglial	
	1	24 V	Operating voltage 24 V
	2	lx+1*	Sensor signal
	3	0 V	Operating voltage 0 V
	4	x*	Sensor signal
	5	Ground	Earth terminal

lx = Input x

*








- [1] CP connection, incoming
- [2] Status LED (green)
- [3] Holder for inscription label (IBS-8x20)
- [4] Red LED for short circuit/overload display
- [5] CP connection, outgoing
- [6] Sensor connections
- [7] Green LED for status indication (one LED per input)

Pin allocation	for sensor	connections	CP-E08-M8-CL

Pin allocation for sensor connections CP-Ed Pin allocation	Pin	Signal	Designation	Pin	Signal
	1	24 V	Operating voltage 24 V	1	24 V
	3	0 V	Operating voltage 0 V	3	0 V
	4	lx*	Sensor signal	4	Ix+1*

* Ix = Input x





- [1] CP connection, incoming
- [2] Status LED (green)
- [3] Holder for inscription label (IBS-8x20)
- [4] Red LED for short circuit/overload display
- [5] CP connection, outgoing
- [6] Sensor connections, plug X2
- [7] Sensor connections,
 - plug X1

in allocation	Pin	Signal	Designation	Pin	Signal	
	Plug X1			Plug X2	2	
	+	24 V DC	Operating voltage	+	24 V DC	- 🗍 - Note
	0	10	Connections for sensors	0	18	8 sensors can be connected to each of the
Put	1	1		1	19	connections X1 and X2.
	2	12		2	I 10	When using the three-row plug PS1-
	3	13		3	11	SAC31-30POL+LED, it is possible to use
	4	14		4	112	the second and third row of contacts for
3 4 +	5	15		5	113	the sensor power supply via a bridge.
	6	16		6	114	
	7	17		7	115	
		0 V DC			0 V DC	
Plug connection for power supply for senso		C31-30POL+LED) tion row 0		Connec	tion row 1	Connection row 2
	-	0 V DC	Operating voltage	-	n.c.	- Bridge
만 모 뜨 [-	7	l x+7	Connections for sensors	7	24 V DC	7 0 V DC
₽₽ ₽ 7	6	l x+6		6		6
	5	l x+5		5		5
[〕 □				4		
	4	l x+4		4		4
	4 3	x+4 x+3		3		3
		-		-	_	
	3	l x+3		3		3
	3 2	x+3 x+2		3	-	3 2

Accessories – Input modules CP-E...-CL

Ordering data					
Designation				Part no.	Туре
Input modules					
	Positive switching			538787	CP-E08-M12-CL
	Positive switching			538788	CP-E08-M8-CL
	Positive switching				
Sensor plug					
	Plug, straight socket, M12x1	5-pin	PG7	175487	SEA-M12-5GS-PG7
		4-pin	PG7	18666	SEA-GS-7
		4-pin	2.5 mm ² O.D.	192008	SEA-4GS-7-2.5
	Plug, straight, M8x1	3-pin	Solderable	18696	SEA-GS-M8
			Screw-in	192009	SEA-3GS-M8-S
	Plug for 2 connecting cables, M12x1, PG11	4-pin		18779	SEA-GS-11-DUO
		5-pin		192010	SEA-5GS-11-DUO
~					
Connection sets for sens	sors				
	Plug, screw-in tension-spring socket with LED	3-row, 30-pin		197162	PS1-SAC31-30POL+LED
Distributors					
- I I I I I I I I I I I I I I I I I I I	Modular system for all types of sensor/actuator dist	ributor		-	NEDY
and the second s					→ Internet: nedy
A CONTRACTOR					
STATES NO.					
Connecting cable					
	Modular system for a choice of connecting cables			_	NEBU
l al	modular system for a choice of connecting capies				→ Internet: nebu
AT ME					- Internet. nebu
C. C					
Protective caps					
	Cover cap for closing off unused connections (10 pie	eces)	For M8 connections	177672	ISK-M8
(AD)			For M12 connections	165592	ISK-M12
Inscription labels					
	Inscription labels 8x20 mm, in frame (20 pieces)			539388	IBS-8x20
	inscription tabels 0x20 mill, in frame (20 pieces)			557500	105-0720
내내내내					
User documentation					
	User documentation for input/output modules		German	539299	P.BECPEA-CL-DE
			English	539300	P.BECPEA-CL-EN
			French	539302	P.BECPEA-CL-FR
			Italian	539303	P.BECPEA-CL-IT
1	1		Snanish	539301	PBF -CPFA-CL-FS

Datasheet - Output modules CP-A08

Function


The electrical outputs control actuators such as individual valves, lamps, signal equipment and much more.

- 🌷 - Note

Optimum actuation of valves with M12 central plug.

Area of application

- Output module with 8 outputs 24 V DC
- M12 connection technology, 5-pin socket
- LED display of the switching status per channel
- Short circuit and overload detection
- Malfunction display by a green LED



General technical data

General technical data			
Туре			CP-A08-M12-5POL
			Positive switching
Number of outputs			8
Allocation of outputs			Single allocation
Output connection type			8x M12, 5-pin
Load voltage connection			M18, 4-pin
Bus connection			2 plugs M9, 5-pin, via prefabricated cables
Max. output current per channe	el	[A]	0.5
Operating voltage		[V DC]	24 ±25%
Load voltage connection		[V DC]	24 ±25%, reverse polarity protected
Fuse protection for power output	ut	[A]	Electronic fuse per output 0.5
Intrinsic current consumption of	of electronics	[mA]	Max. 90
Overload/short circuit protection	on		Per channel
Switching logic			PNP to IEC 1131-2
Degree of protection to EN 605	29		IP65 (when fully plugged in or fitted with protective cover)
Temperature range	Operation	[°C]	-5 +50
	Storage	[°C]	-20 +70
Material			Die-cast aluminium
PWIS conformity			VDMA24364-B2-L
Dimensions (LxWxD)		[mm]	172.9 x 78 x 57.1
Weight		[g]	500

Certifications


ATEX category for gas	II 3G
Type of ignition protection for gas	Ex nA IIC T5 X Gc
ATEX category for dust	II 3D
Type of ignition protection for dust	Ex tc IIIC T80°C X Dc IP65
ATEX ambient temperature [°C]	-5 ≤ Ta ≤ +50
CE marking (see declaration of conformity)	To EU EMC Directive ¹⁾
	To EU Explosion Protection Directive (ATEX)
KC mark	KC EMC
Certification	c UL us - Recognized (OL)

1) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Datasheet - Output modules CP-A08

Connection and display components CP-A08-M12...



[1] Load voltage	connection
------------------	------------

- [2] CP connection, incoming
- [3] Slot for identification labels (IBS-6x10)
- [4] Identification for output type:
- OUTPUT-P for PNP outputs
- OUTPUT-N for NPN outputs
- [5] Status LED (green)
- [6] CP connection, outgoing
- [7] Connections for actuators
- [8] Yellow LED for status display (one LED per input)

	Pin	Signal	Designation
2	1	n.c.	Not connected
	2	24 V DC ±25%	Operating voltage
	3	0 V	Operating voltage 0 V
	4	FE	Protective earthing
n allocation for outputs			

Thratocation	1.00	Signat	Designation		Signat		
CP-A08-M12-5POL (PNP outputs)							
	1	n.c.	Not connected	1	n.c.		
	2	0x+1	Connected with pin 4 of	2	n.c.	- 📲 - Note	
			plug 2/not connected			Two outputs can be connected to connec-	
	3	0 V	Reference potential	3	0 V	tions 0, 2, 4 and 6 of the CP output mod-	
	4	Ox	Output/connected with	4	0x+1	ule via an internal connection between	
Ax Ax+1			pin 2 of plug 1			pin 2 of the even numbered output and	
	5	Ground	Earth terminal	5	Ground	pin 4 of the opposite odd numbered	
						output.	

Ox = Output x

*

mastion CD A09 M12

Accessories – Output modules CP-A08

Ordering data					1-
Designation				Part no.	Туре
Output modules	1		_		1
	Positive switching	175640	CP-A08-M12-5POL		
Power supply					
	Power supply socket, straight, M18x1, 4-pin		For 1.5 mm ²	18493	NTSD-GD-9
			For 2.5 mm ²	18526	NTSD-GD-13.5
	Power supply socket, angled, M18x1, 4-pin		For 1.5 mm ²	18527	NTSD-WD-9
		For 2.5 mm ²		533119	NTSD-WD-11
Sensor plug					
	Plug, straight socket, M12x1	5-pin		175487	SEA-M12-5GS-PG7
	Plug for 2 connecting cables, M12x1, PG11	4-pin		18779	SEA-GS-11-DUO
		5-pin		192010	SEA-5GS-11-DUO
Distributors					
STATE OF STATE	Modular system for all types of sensor/actuator distributor			-	NEDY → Internet: nedy
Connecting cable					
	Modular system for a choice of connecting cables			-	NEBU → Internet: nebu
Mounting					
	Mounting for H-rail			170169	CP-TS-HS35
	Mounting for H-rail			1/0109	CC-1-3-11-3-3

Datasheet – Output modules CP-A08-EL

Function

The electrical outputs control actuators such as individual valves, lamps, signal equipment and much more.

- 🕴 - Note

The output module is ideal for actuation of valves with M12 central plug.

Area of application

- Output module with 8 outputs 24 V DC
- M12, 5-pin connection technologyDisplay of the switching status per
- channel via LEDShort circuit and overload detection
- Malfunction display by a red LED
- Module supports the CPI functionality (only in combination with the CPX CP interface)
- Circumferential labelling with large, hinged inscription label
- Earthing plate and H-rail mounting already integrated



General technical data

Туре		CP-A08-M12-EL-Z
		Positive switching
Number of outputs		8
Allocation of outputs		Connection 1, 3, 5 and 7 with double allocation, connection 2, 4, 6 and 8 with single
		allocation
Sensor connection type		8x M12, 5-pin
Power supply 24 V DC		M12, 4-pin, A-coded
Intrinsic current consumption at operating voltage	[mA]	Typically 35
Max. aggregate current per module	[A]	4
Max. output current per channel	[A]	Max. 0.5, max. 2 outputs can be connected in parallel
Nominal operating voltage	[V DC]	24
Operating voltage range	[V DC]	18 30
Residual ripple load voltage	[Vss]	4
Note concerning load voltage		Via load voltage connection (24 V DC)
Fuse protection (short circuit)		Internal electronic fuse protection for each group
Switching logic		PNP
Output characteristic		To ICE 1131-T2
Electrical isolation between channels		None
Connection to bus node		Via pre-assembled cables
Diagnostics		CP communication
		Short circuit/overload per channel
		Undervoltage
LED displays		3 module diagnostics
		8 channel status
		8 channel diagnostics

Materials	
Housing	Reinforced PA
Cover	Reinforced PA
Note on materials	RoHS-compliant
PWIS conformity	VDMA24364-B2-L

Datasheet - Output modules CP-A08-EL

Operating and environmental conditions

Degree of protection to EN 60529		IP65/IP67 (when fully plugged in or fitted with protective cap)
Ambient temperature	[°C]	-5+50
Storage temperature	[°C]	-20 +70
Corrosion resistance class CRC ¹⁾		1
CE marking (see declaration of conformity)		To EU EMC Directive ²⁾
		To EU RoHS Directive ²⁾
UKCA marking (see declaration of conformity)		To UK instructions for EMC ²⁾
		To UK RoHS instructions ²⁾
KC mark		KC EMC
Certification		c UL us listed (OL)
		RCM mark
		C-Tick


1) More information: www.festo.com/x/topic/kbk


2) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... -> Support/Downloads.


If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Connection and display components











- [2] CP connection, incoming
- [3] Status LED (module) for short circuit/overload of sensor supply (red)
- [4] Status LED for CP communication (green)
- [5] Status LED for load supply (PL, green)
- [6] Status LEDs for outputs (status display, yellow)
- [7] Status LED for output (channel) short circuit/overload (red)
- [8] Fixture for inscription label holder ASCF-H-E2
- [9] 8 outputs (1 output per socket)

Pin	Signal	Designation
1	n.c.	Not connected
2	24 V DC ±25%	Operating voltage
3	0 V	Operating voltage 0 V
4	FE	Protective earthing

Datasheet - Output modules CP-A08-EL



* Ox = Output x



Ox = Output x

Accessories – Output modules CP-A08-EL

Ordering data				1-	1-
Designation				Part no.	Туре
Output module				. <u> </u>	
	Positive switching			546924	CP-A08-M12-EL-Z
Plug					
	Plug, straight socket, M12x1	5-pin	PG7	175487	SEA-M12-5GS-PG7
		4-pin	PG7	18666	SEA-GS-7
		4-pin	2.5 mm ² 0.D.	192008	SEA-4GS-7-2.5
	Plug for 2 connecting cables, M12x1, PG11	4-pin		18779	SEA-GS-11-DUO
		5-pin		192010	SEA-5GS-11-DUO
Distributors					
STREET, STREET	Modular system for all types of sensor/actuator distrib	utor		-	NEDY → Internet: nedy
Inscription label holders					
1	Inscription label holders for EL modules, bag of 10			547473	ASCF-H-E2
User documentation					
	User documentation for input/output modules		German	539299	P.BECPEA-CL-DE
			English	539300	P.BECPEA-CL-EN
			French	539302	P.BECPEA-CL-FR
			Italian	539303	P.BECPEA-CL-IT
			Spanish	539301	P.BECPEA-CL-ES

Datasheet - Output modules CP-A04

Function

The electrical outputs control actuators such as individual valves, lamps, signal equipment and much more.

Area of application

- Output module with 4 outputs 24 V DC
- M12 connection technology, with 5-pin sockets
- LED display of the switching status per channel
- Short circuit and overload detection
- Malfunction display by a red LED
- Module supports the CPI functionality (only in combination with the CPX CP interface)



General technical data		
Туре		CP-A04-M12-CL Positive switching
Number of outputs		4
Allocation of outputs		Connection 1 and 3 with double allocation, connection 2 and 4 with single allocation
Sensor connection type	·	4x M12, 5-pin
Power supply 24 V DC		From the bus node, basic unit, CP interface, etc.
Intrinsic current consumption of electronics	[mA]	Typically 35
Max. output current per channel	[A]	Max. 0.5, max. 2 outputs can be connected in parallel
Operating voltage	[V DC]	24 ±25%
Fuse protection for power output		Internal electronic short-circuit protection per output
Switching logic		PNP
Output characteristic		To ICE 1131-2
Galvanic isolation		None
Connection to bus node		Via pre-assembled cables
Diagnostics		Undervoltage
		Short circuit at actuator output (per channel)
PWIS conformity		VDMA24364-B2-L
Dimensions (LxWxD)	[mm]	151 x 30 x 25
Weight	[g]	165

- Jorimum actuation of ur

Optimum actuation of valves with M12 central plug.

Datasheet – Output modules CP-A04

Operating and environmental conditions

Degree of protection to EN 60529		IP65/IP67 (when fully plugged in or fitted with protective cap)
Ambient temperature	[°C]	-5 +50
Storage temperature	[°C]	-20 +70
Corrosion resistance class CRC ¹⁾		1
CE marking (see declaration of conformity)		To EU EMC Directive ²⁾
		To EU RoHS Directive
		To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity)		To UK instructions for EMC
		To UK RoHS instructions
		To UK EX instructions
KC mark		KC EMC
Certification		c UL us listed (OL)
		RCM

More information: www.festo.com/x/topic/kbk
 For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.


ATEX certifications	
ATEX category for gas	II 3G
Type of ignition protection for gas	Ex ec IIC T6 Gc X
ATEX category for dust	II 3D
Type of ignition protection for dust	Ex tc IIIC T70°C IP67 Dc X
ATEX ambient temperature [°C]	-5 ≤ Ta ≤ +50
Explosion protection certification outside the EU	EPL Dc (GB)
	EPL Gc (GB)

-- Note

When operating device combinations in potentially explosive areas, the lowest common zone, temperature class and ambient temperature of the individual devices determine the possible use of the entire module.

Datasheet - Output modules CP-A04

Connection and display components CP-A04-M12-CL



	Pin	Signal		Pin	Signal	
CP-A08-M12-5POL (PNP outputs)						
	1	n.c.	Not connected	1	n.c.	「 _
	2	0x+1	Connected with pin 4 of	2	n.c.	- 闄 - Note
			plug 2/not connected			Two outputs can be connected to each of
	3	0 V	Reference potential	3	0 V	connections 1 and 3 of the CP output
	4	Ox	Output/connected with	4	Ox+1	module via an internal connection
			pin 2 of plug 1			between pin 2 of the odd numbered
	5	FE	Earth terminal	5	FE	output and pin 4 of the underlying even
						numbered output.

* Ox = Output x


Accessories – Output modules CP-A04

Ordering data – Accesso	pries				
Designation				Part no.	Туре
Output module					
	Positive switching			538790	CP-A04-M12-CL
Sensor plug					
	Plug, straight socket, M12x1	5-pin	PG7	175487	SEA-M12-5GS-PG7
		4-pin	PG7	18666	SEA-GS-7
		4-pin	2.5 mm ² O.D.	192008	SEA-4GS-7-2.5
	Plug for 2 connecting cables, M12x1, PG11	4-pin		18779	SEA-GS-11-DUO
		5-pin		192010	SEA-5GS-11-DUO
Distributors					
U.S. S.	Modular system for all types of sensor/actuator distributor				NEDY → Internet: nedy
Connecting cable				1	
STATE OF	Modular system for a choice of connecting cables				NEBU → Internet: nebu
Protective caps				-	
	Cover cap for closing off unused connections (10 pieces) For M12 connections				ISK-M12
Inscription labels					
	Inscription labels 8x20 mm, in frame (20 pieces)			539388	IBS-8x20
User documentation					
	User documentation for input/output modules		German	539299	P.BECPEA-CL-DE
			English	539300	P.BECPEA-CL-EN
			French	539302	P.BECPEA-CL-FR
			Italian	539303	P.BECPEA-CL-IT
			Spanish	539301	P.BECPEA-CL-ES

Datasheet - Valve terminals MPA-S

- 11 Flow rate

MPA1: up to 360 l/min MPA14: up to 550 l/min MPA2: up to 700 l/min



. 4 Voltage 24 V DC

₋Ӷӏ₋

CPI interface for communication between a valve terminal MPA-S and a CPI master. It activates a valve terminal MPA-S with up to 32 solenoid coils on max. 16 valve positions. It is also possible to install an additional electrical supply at any other point on the valve terminal to create different voltage zones.



Note

An additional electrical supply is essential for more than 16 MPA2 solenoid coils (more than 4 electronics modules).

Please note that without an additional electrical supply a maximum of 24 solenoid coils can be connected at the same time.

If more than 24 MPA1, 24 MPA14 or 12 MPA2 solenoid coils are to be connected at the same time, an additional supply must be connected at the latest after the third electronics module.

General technical data
Туре
CP interface, incoming

Туре			MPA-CPI-VI
CP interface, incoming			Plug M9, 5-pin
CP interface, outgoing			M9 socket, 5-pin
Max. no. of valve positions			32
Max. number of pressure zones			9
LED display (product-specific)	PS		Common message regarding power supply
	PL		Power supply for valves
	Symbol		Module error
Nominal operating voltage		[V DC]	24
Permissible voltage fluctuations		[V DC]	±25%
Power failure buffering	Logic side only	[ms]	10
Current consumption at nominal operating	Load	[mA]	Dependent on valve type and number of valves
voltage	Electronics	[mA]	Approx. 50 (plus current consumption of electronics modules)
Residual ripple		[Vss]	4
Materials			Die-cast aluminium, PA
Note on materials			RoHS-compliant
PWIS conformity			VDMA24364-B1/B2-L
Dimensions			→ Internet: mpa-s
Weight		[g]	220
Technical data on valves			→ Internet: mpa-s
Degree of protection			IP67

Datasheet - Valve terminals MPA-S

Operating and environmental conditions


operating and environmental conditions		
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[MPa]	-0.09+1
	[bar]	-0.9 +10
Pilot pressure	[MPa]	0.3 0.8
	[bar]	38
Ambient temperature	[°C]	-5 +50
Temperature of medium	[°C]	-5 +50
Storage temperature	[°C]	-20 +40
Relative humidity		Max. 90% at 40°C
CE marking (see declaration of conformity)		To EU EMC Directive ¹⁾
		To EU RoHS Directive
		To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity)		To UK instructions for EMC
		To UK RoHS instructions
		To UK EX instructions
KC mark		KC EMC
Certification		c UL us - Recognized (OL)
		RCM

1) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/...→ Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

ATEX		
ATEX category for gas		II 3G
Type of ignition protection for gas		Ex ec IIC T4 Gc X
Explosion-proof ambient temperature	[°C]	-5 ≤ Ta ≤ +50
Explosion protection certification outside the EU		EPL Dc (GB)
		EPL Gc (GB)

Connection and display components



- [1] CP connection, incoming
- [2] CP connection, outgoing
- [3] Status LEDs
 - CP system supply (green) Load supply (green) Module fault (red)

Datasheet – Valve terminals MPA-S


Ordering data Designation			Part no.	Туре
Valve terminal MPA-S				
	With CPI interface		546280	MPA-CPI-VI
Valve terminal connection	n			
	Connecting cable WS-WD	0.25 m	540327	KVI-CP-3-WS-WD-0.25
		0.5 m	540328	KVI-CP-3-WS-WD-0.5
		2 m	540329	KVI-CP-3-WS-WD-2
		5 m	540330	KVI-CP-3-WS-WD-5
		8 m	540331	KVI-CP-3-WS-WD-8
	Connecting cable GS-GD	2 m	540332	KVI-CP-3-GS-GD-2
Mar 20		5 m	540333	KVI-CP-3-GS-GD-5
CO MI-		8 m	540334	KVI-CP-3-GS-GD-8

Datasheet - CPV-SC valve terminals

- N - Flow rate 170 l/min

- **[]** - Valve width 10 mm

- **L** - Voltage 24 V DC CPI interface for communication between a CPV-SC valve terminal and a CPI master. It activates a valve terminal CPV-SC with up to 16 solenoid coils.



General technical data				
Туре			CPVSC1-AE16-CPI	
Types of communication		-	CP fieldbus	
Log			CP fieldbus	
Fieldbus interface			M9, 5-pin, plug and socket	
Max. no. of solenoid coils			16	
LED display (bus-specific)			CP: CP fieldbus	
Device-specific diagnostics			Undervoltage of valve terminal	
Parameterisation			Parameterisation via CP protocol	
Reverse-polarity protection			For all electrical operating voltage connections	
Current consumption at nominal operating voltage	Electronics	[mA]	≤100	
	Load		Dependent on valve type and number of valves	
Protection against direct and indirect contact			PELV	
Housing material			Reinforced PA	
Note on materials			RoHS-compliant	
PWIS conformity			VDMA24364-B2-L	
Type of mounting			Via through-hole	
Width		[mm]	52	
Height		[mm]	40	
Length [mm]		70		
Product weight [g]		150		
Technical data on valves			→ Internet: cpv-sc	
Degree of protection			IP20	
			To IEC 60529	

Datasheet - CPV-SC valve terminals

Operating and environmental conditions


Ambient temperature	[°C]	-5 +50
Storage temperature	[°C]	-20 +50
Relative humidity		90% at 50°C
		Non-condensing
Corrosion resistance class CRC ¹⁾		1
CE marking (see declaration of conformity)		To EU EMC Directive ²⁾
Certification		c UL us - Recognized (OL)

1) More information: www.festo.com/x/topic/kbk

2) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... -> Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Connection and display components



- $[1] \quad {\sf CP} \ {\sf connection, incoming} \\$
- [2] CP connection, outgoing
- [3] Status LED for CP communication
- [4] Status LEDs for valves

Ordering data Designation			Part no.	Туре
Valve terminal CPV-SC				
	With CPI interface		541975	CPVSC1-AE16-CPI
/alve terminal connectio		1		
	Connecting cable WS-WD	0.25 m	540327	KVI-CP-3-WS-WD-0.25
		0.5 m	540328	KVI-CP-3-WS-WD-0.5
		2 m	540329	KVI-CP-3-WS-WD-2
		5 m	540330	KVI-CP-3-WS-WD-5
		8 m	540331	KVI-CP-3-WS-WD-8
	Connecting cable GS-GD	2 m	540332	KVI-CP-3-GS-GD-2
Mar 20		5 m	540333	KVI-CP-3-GS-GD-5
and the second s		8 m	540334	KVI-CP-3-GS-GD-8

T

I


Datasheet – Bus node CTEU

- N Flow rate Dependent on the connected valve terminal
- **[]** Valve width Dependent on the connected valve terminal
- **L** Voltage 24 V DC

CPI interface for communication between a valve terminal or input modules with I-Port interface and a CPI master.

Valve terminals with I-Port interface
• CPV

- MPA-L
- VTUG



General technical data

General technical data				
Туре			CTEU-CP	
Log			CPI-B	
Diagnostics			Communication error	
			System diagnostics	
			Undervoltage	
Parameterisation			Diagnostic behaviour	
			Fail-safe response	
Configuration support			None	
Control elements			DIL switch	
LED display	Product-specific		PS: Operating voltage for electronics and load supply	
			X1: System status of module at I-Port 1	
			X2: System status of module at I-Port 2	
	Bus-specific		RUN: Communication OK	
Maximum address capacity	Inputs	[byte]	4	
	Outputs	[byte]	4	
Type of mounting			On electrical interface	
			On electrical connection block	
Degree of protection			IP65	
			IP67	
Note on degree of protection			In assembled state	
			Unused connections sealed	
Dimensions W x L x H		[mm]	40 x 91 x 50	
Grid dimension		[mm]	40	
Product weight		[g]	105	

Technical data Fieldbus interface

Fieldbus interface	
Log	CPI-B
Function	Incoming bus connection
	Power supply
Transmission rate [kbps]	1000
Туре	CP installation system
Connection type	Plug
Connection technology	M9x0.5
Number of pins/wires	5
Internal cycle time	2 ms per 2 bytes of user data
Fieldbus interface 2	
Function	Bus connection outgoing
	Power supply
Connection type	Socket
Connection technology	M9x0.5
Number of pins/wires	5

Datasheet - Bus node CTEU

Technical data – Electrics

Nominal operating voltage	[V DC]	24
Operating voltage range	[V DC]	18 30
Intrinsic current consumption at nominal operating voltage	[mA]	Typically 50
Max. power supply	[A]	3.4
Power failure buffering	[ms]	10

Operating and environmental conditions

Ambient temperature	[°C]	-5+50
Storage temperature	[°C]	-20 +70
Corrosion resistance class CRC ¹⁾		2
CE marking (see declaration of conformity)		To EU EMC Directive ²⁾
		To EU RoHS Directive
UKCA marking (see declaration of conformity)		To UK instructions for EMC
		To UK RoHS instructions
KC mark		KC EMC
Certification		c UL us - Listed (OL)
		RCM


1) More information: www.festo.com/x/topic/kbk

2) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... -> Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Materials	
Housing	PA
Note on materials	RoHS-compliant
PWIS conformity	VDMA24364 zone III

Connection and display components




- [1] CP connection, incoming
- [2] CP connection, outgoing
- [3] Status LED for CP communication
- [4] DIL switch

I


Datasheet – Bus node CTEU

Ordering data					
Designation			Part no.	Туре	
Bus node					
	For valve terminals with I-Port interface		2149714	CTEU-CP	
Valve terminal connecti	00				
	Connecting cable WS-WD	0.25 m	540327	KVI-CP-3-WS-WD-0.25	
		0.5 m	540328	KVI-CP-3-WS-WD-0.5	
		2 m	540329	KVI-CP-3-WS-WD-2	
		5 m	540330	KVI-CP-3-WS-WD-5	
		8 m	540331	KVI-CP-3-WS-WD-8	
	Connecting cable GS-GD	2 m	540332	KVI-CP-3-GS-GD-2	
STATE SC		5 m	540333	KVI-CP-3-GS-GD-5	
THE THE		8 m	540334	KVI-CP-3-GS-GD-8	

Technical data



Technical data



 \mathbb{O}

[1] Slots for inscription labels

192.9 207.9 ±0.4 216.9

[2] Earthing screw M3


[3] Protective caps (included in the

scope of delivery)


63


[4] H-rail with support base

Technical data



Technical data






- [1] Through-hole for surface mounting
- [2] H-rail
- [3] Mounting kit for H-rail (included in the scope of delivery)

32.81

Technical data




- [1] Through-hole for surface mounting
- [2] H-rail
- [3] Mounting kit for H-rail (included in the scope of delivery)


 $\left[1\right]$

Download CAD data → <u>www.festo.com</u>


Technical data



CP-E08-M8-CL



CP-E16-KL-CL



Order processing information

Configuration guidelines

5 5			
The CPI system supports a certain number of modules per CP string de- pending on the type of the CP master and the	CP modules connected.	CP masters and CP modules can be split into two different groups:	With CPI functionalityWithout CPI functionality.
CP modules with CPI functionality		CP modules without CPI functionality	
CP modules with CPI functionality offer the following features:Incoming and outgoing CP interfaceAny arrangement of the modules within a CP string	 Max. 4 modules per CP string Max. 32 inputs and 32 outputs can be connected to each string de- pending on the version 	Sturdy CP modules offer the following features:CP valve terminals and CP output modules have an incoming and outgoing CP interface	 CP input modules only have an incoming CP interface and therefore can only be positioned at the end of a CP string All CP modules with CPI functionalitic can also be connected to CP master without extended functionality.
Information on using CP modules with a	nd without CPI functionality		
A mixture of CP modules with and with- out CPI functionality is possible. The following must be noted in this case:	 Only one input module without CPI functionality is possible per CP string (at the end of a CP string) 	• Only one CP valve terminal or output module without CPI functionality is possible per CP string (any point in the CP string)	• Free positions in the CP string can be filled by CP modules with CPI functionality (max. 4 modules).
 Note The cable length for any given string may not exceed 10 m. 	No more than 32 inputs and 32 out- puts (sum of all 4 CP modules on a CP string) may be connected, regard- less of the type of CP module (with or		

Connecting cables are available with lengths of 0.25 m, 0.5 m, 2 m, 5 m $\,$ and 8 m → p. 69

less of the type of CP module (with or without CPI functionality).

Accessories

Ordering data Designation					Part no.	Туре
Connection sets for pov	ver supply and sensors					
	Plug, screw-in tension-spri	ng socket	3-row, 30-pin	With LED	197162	PS1-SAC31-30POL+LED
Sensor plug						
	Plug M8, 3-pin	Solderable	For NEDY-L2R1-V1-M8G3	-N-M8G4	18696	SEA-GS-M8
		Screw-in	For NEDY-L2R1-V1-M8G3	-N-M8G4	192009	SEA-3GS-M8-S
	Plug M12, 4-pin	Screw terminal	For cable Ø 2.5 2.9 mr	n	192008	SEA-4GS-7-2.5
			For 2x cable Ø 3 5 mm		18779	SEA-GS-11-DUO
			For cable Ø 4 6 mm		18666	SEA-GS-7
	Plug, M12, 5-pin	Screw terminal	For 2x cable Ø 2.5 5 m	m	192010	SEA-5GS-11-DUO
			For cable Ø 4 6 mm		175487	SEA-M12-5GS-PG7
istributors			I			
LAND TO THE OWNER	Modular system for all type	s of sensor/actuator dis	tributor		-	NEDY → Internet: nedy
	Push-in T-connector	1x plug M8, 4-pin	2x socket M8, 3-pin		8005312	NEDY-L2R1-V1-M8G3-N-M8G4
		1x plug M12, 4-pin	2x socket M8, 3-pin		8005311	NEDY-L2R1-V1-M8G3-N-M12G4
			2x socket M12, 5-pin		8005310	NEDY-L2R1-V1-M12G5-N-M12G4
Connecting cable	• •	-				
	Connecting cable M8-M8	3-pin	Straight plug/straight	0.5 m	541346	NEBU-M8G3-K-0.5-M8G3
a se	Ū,		socket	1.0 m	541347	NEBU-M8G3-K-1-M8G3
				2.5 m	541348	NEBU-M8G3-K-2.5-M8G3
A SULLING				5.0 m	541349	NEBU-M8G3-K-5-M8G3
	Connecting cable	5-pin	Straight plug/straight	1.5 m	529044	KV-M12-M12-1.5
	M12-M12		socket	3.5 m	530901	KV-M12-M12-3.5
	Modular system for a choic	e of connecting cables		-	-	NEBU → Internet: nebu
onnecting cable – CP r	modulos					
	Angled plug/angled socket			0.25 m	540327	KVI-CP-3-WS-WD-0.25
a start	אוואופובע אועצ/מווצובע גענגענ			0.25 m	540327	KVI-CP-3-WS-WD-0.25
Í MÍ				2 m	540329	KVI-CP-3-WS-WD-2
				5 m	540329	KVI-CP-3-WS-WD-5
		8 m				KVI-CP-3-WS-WD-8
	Straight plug/straight sock	et	2 m		540331 540332	KVI-CP-3-GS-GD-2
MI DO		5 m			540333	KVI-CP-3-GS-GD-5
a Minut				8 m	540334	KVI-CP-3-GS-GD-8
	Connecting plug for CP cab	le (cabinet through-feed)	1	543252	KVI-CP-3-SSD
OT Mar						

Accessories

Ordering data			1	1
Designation			Part no.	Туре
Protective caps				
	Cover cap for closing off unused connections (10 pieces)	For M8 connections	177672	ISK-M8
		For M12 connections	165592	ISK-M12
Mounting componen				
	Mounting for H-rail, CP modules		170169	CP-TS-HS35
nscription labels				
	Inscription labels 6x10 mm, in frame (64 pieces)			IBS-6x10
	Inscription labels 8x20 mm in frames (20 pieces) for compact mode	n labels 8x20 mm in frames (20 pieces) for compact modules (CPCL)		IBS-8x20
	Inscription label holders for EL modules, bag of 10	ription label holders for EL modules, bag of 10		
Documentation				
	User documentation for CPX-CP interface	German	539293	P.BE-CPX-CP-EN
		English	539294	P.BE-CPX-CP-EN
		Spanish	539295	P.BE-CPX-CP-ES
\sim		French	539296	P.BE-CPX-CP-FR
		Italian	539297	P.BE-CPX-CP-IT
	User documentation for compact input/output modules	German	539299	P.BECPEA-CL-DE
		English	539300	P.BECPEA-CL-EN
		French	539302	P.BECPEA-CL-FR
		Italian	539303	P.BECPEA-CL-IT
		Spanish	539301	P.BECPEA-CL-ES
	System description	German	165126	P.BE-CPSYS-DE
		English	165226	P.BE-CPSYS-EN
		French	165128	P.BE-CPSYS-FR
		Italian	165158	P.BE-CPSYS-IT
		Spanish	165228	P.BE-CPSYS-ES
		Spanish	10,220	