

Short-stroke cylinders ADNE-LAS, with linear motor



# Short-stroke cylinders ADNE-LAS, with linear motor

Key features

At a glance		
Properties		Range of applications
<ul style="list-style-type: none"> <li>• Electric short-stroke cylinder with integrated linear motor, specifically designed for dynamic movements between two end positions</li> <li>• A cycle of advancing and retracing motion over 15 mm can be achieved in 64 ms (movement frequency of up to 13.6 Hz)</li> </ul>	<ul style="list-style-type: none"> <li>• Festo plug &amp; work: connect, switch on, teach-in end positions and then the system is ready to use. There is no need to set servo parameters</li> <li>• Mechanical interfaces are largely compatible with the pneumatic compact cylinder ADN</li> </ul>	<ul style="list-style-type: none"> <li>• Electronic end-position cushioning, i.e. constant force across the entire stroke with the force only reduced at the end positions as end-position cushioning</li> <li>• No external magnetic fields</li> </ul>
		<ul style="list-style-type: none"> <li>• Dynamic movement with secondary accuracy requirements:               <ul style="list-style-type: none"> <li>– Switching deflectors</li> <li>– Rejecting good/bad parts from an ongoing production process</li> <li>– Blocking movements</li> <li>– Checking switches</li> <li>– Applying labels</li> </ul> </li> </ul>

## Everything from a single source

Short-stroke cylinder  
ADNE-LAS

→ 3



End-position controller  
CMFL

→ Internet: cmfl

- Short-stroke cylinder ADNE-LAS
- End-position controller CMFL
- Motor cable NEBM
- Power supply cable KPWR
- Pilot line KES

The short-stroke cylinder ADNE-LAS and the end-position controller CMFL form one unit. Only one cable is required between the short-stroke cylinder and end-position controller.


## Movement pattern

Four movement patterns can be selected via inputs.

- |  |  |
|--|--|
| 1. Advancing                           |  |
| 2. Retracting                          |  |
| 3. Advancing and then retracting again |  |
| 4. Retracting and then advancing again |  |

# Short-stroke cylinders ADNE-LAS, with linear motor


Type codes



# Short-stroke cylinders ADNE-LAS, with linear motor

Peripherals overview

FESTO



# Short-stroke cylinders ADNE-LAS, with linear motor


Peripherals overview

Mounting attachments and accessories					
	Brief description	Variant		→ Page/Internet	
		Basic version	S20		
1	Foot mounting HNA	For bearing or end caps	■	■	15
2	Flange mounting FNC	For bearing or end caps	■	■	15
3	Trunnion flange ZNCF	For bearing or end caps	■	■	17
4	Swivel flange SNCL	For end caps	■	–	16
5	Swivel flange SNCB	For end caps	■	–	16
6	Swivel flange SNCS	For end caps, with spherical bearing	■	–	17
7	Trunnion support LNZG	In combination with trunnion flange ZNCF	■	■	18
8	Clevis foot LNG	In combination with swivel flange SNCB	■	–	18
9	Clevis foot LBG	In combination with swivel flange SNCS	■	–	18
10	Rod eye SGS	With spherical bearing	■	■	18
11	Coupling piece KSZ	Compensates radial misalignments up to ±1 mm	■	■	18
12	Adapter AD	Specially for through, hollow piston rods, for example for connecting vacuum generators	■	■	18
13	Rod clevis SG	–	■	■	18
14	Self-aligning rod coupler FK	Compensates radial and angular misalignments	■	■	18
15	End-position controller CMFL	For parameterising and positioning the short-stroke cylinder	■	■	cmfl
16	Power supply cable KPWR	For connecting the load and logic supply	■	■	cmfl
17	Pilot line KES	For I/O interface to any controller	■	■	cmfl
18	Motor cable NEBM	For connecting the motor and end-position controller	■	■	cmfl

# Short-stroke cylinders ADNE-LAS, with linear motor

Technical data

Function



Size  
32, 40

Stroke length  
15 ... 45 mm

Note

All values are based on a standard temperature of 23 °C. Dynamic response and accuracy are dependent on the mounting (rigidity) and the derivation of the thermal energy (heat concentration).



General technical data					
Size		32		40	
Stroke	[mm]	15	35	20	45
Design		Electric linear direct drive			
		Electric cylinder with piston rod			
Based on standard		ISO 21287			
Type of mounting		Via female thread			
		Via accessories			
Mounting position		Horizontal			
Minimum stroke	[mm]	7.5	17.5	10	22.5
Max. effective load	[g]	500			
Max. speed	[m/s]	1.9	1.8	1.5	1.6
Repetition accuracy	[mm]	±0.1			


Mechanical data						
Size		32		40		
Stroke	[mm]	15	35	20	45	
Deflection of piston rod <sup>1)</sup>	Retracted	[mm]	0.14	0.14	0.15	0.15
	Advanced	[mm]	0.25	0.35	0.25	0.50
At operating voltage of 48 V						
Continuous feed force <sup>2)</sup>	[N]	10.5	5.9	14.2	11	
Peak feed force	[N]	26	15	51	30	
Holding force in the end positions	[N]	3	2	6	4.5	
At operating voltage of 24 V						
Continuous feed force <sup>2)</sup>	[N]	10.5	5.9	14.2	11	
Peak feed force	[N]	13	8	28	16	
Holding force in the end positions	[N]	3	2	6	4.5	

1) In new condition

2) Measured at a motor temperature of 70 °C

Note

Due to the maximum effective load of 500 g, the lateral force  $F_q$  of max. 5 N must not be exceeded.



No torques are permissible on the piston rod.

# Short-stroke cylinders ADNE-LAS, with linear motor

Technical data

Electrical data	
Motor type	Linear AC synchronous motor
End-position detection	Internal, non-contacting
Magnetic radiation	None

Operating and environmental conditions	
Ambient temperature	[°C] 0 ... +40
Motor temperature during teach-in procedure	[°C] +15 ... +50
Max. motor temperature	[°C] 70 (shuts down at 75 °C/in the event of a malfunction over 100 °C)
Standard temperature <sup>1)</sup>	[°C] 23
Temperature monitoring	Shuts down if motor overheats
Storage temperature	[°C] -20 ... +60
Protection class (mechanical system)	IP40
Protection class (electrical connection)	IP65
Relative air humidity (non-condensing)	[%] 95
CE marking (see declaration of conformity)	To EU EMC Directive
Certification	C-Tick
Corrosion resistance class CRC <sup>2)</sup>	2

1) Unless otherwise stated, all values are based on standard temperature.

2) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.


Weight [g]					
Size		32		40	
Stroke	[mm]	15	35	20	45
Product weight		710	940	1260	1710
	S20	725	960	1290	1750
Moving load		105	130	275	350
	S20	120	150	305	390

# Short-stroke cylinders ADNE-LAS, with linear motor

Technical data


## Materials

Sectional view



Short-stroke cylinder	
1	Piston rod High-alloy stainless steel
2	Bearing cap Anodised wrought aluminium alloy
3	Housing Anodised wrought aluminium alloy
4	Connector cap Anodised wrought aluminium alloy
5	Cover Anodised wrought aluminium alloy
-	Plain bearing Polyacetal
-	Screws, nuts Steel
Note on materials Contains PWIS (paint-wetting impairment substances) RoHS-compliant	

## Internal cushioning



1 Working stroke:  
The recommended, available operating range

2 Cushioning length:  
The distance from the end positions of the working stroke to the mechanical end position

3 Rebound:  
How far the drive rebounds depends on the load, the dynamics of the movement and the temperature of the cylinder

Size		32	40
Stroke	[mm]	15	20
Working stroke	[mm]	15	20
Minimum stroke	[mm]	7.5	10
Cushioning length	[mm]	0.7	0.8
Rebound at 48 V <sup>1)</sup>	[mm]	0.8	0.5
Rebound at 24 V <sup>1)</sup>	[mm]	0.3	0.5


1) Repeat the teach-in procedure if the rebound is too strong.



# Short-stroke cylinders ADNE-LAS, with linear motor

Technical data

## Max. frequency $f$ as a function of effective load $m$ and voltage $U$ , briefly




Size	32		40		
Stroke [mm]	15	35	20	45	
At operating voltage of 48 V					
Frequency	Effective load = 0 g [Hz]	13.6	7.1	11.6	5.1
	Effective load = 250 g [Hz]	7.2	5.8	8.9	4.9
	Effective load = 500 g [Hz]	4.7	4.5	7	4.1
At operating voltage of 24 V					
Frequency	Effective load = 0 g [Hz]	11.1	5.5	8.8	4.2
	Effective load = 250 g [Hz]	9.1	4.7	7.2	3.9
	Effective load = 500 g [Hz]	6	3.2	5.4	3


- - Note

Applies to a motor temperature up to max. 74 °C.

## Frequency $f$ as a function of effective load $m$ and voltage $U$ , during continuous operation




At  $U = 48\text{ V}$   
ADNE-32-15/35




— ADNE-32-15  
- - - ADNE-32-35

At  $U = 24\text{ V}$   
ADNE-32-15/35




— ADNE-32-15  
- - - ADNE-32-35

ADNE-40-20/45



— ADNE-40-20  
- - - ADNE-40-45

ADNE-40-20/45




— ADNE-40-20  
- - - ADNE-40-45

# Short-stroke cylinders ADNE-LAS, with linear motor


Technical data

## Min. positioning time $t$ as a function of voltage $U$ , at an effective load of 0 g




Size	32		40	
Stroke [mm]	15	35	20	45
At operating voltage of 48 V				
Positioning time [ms]	30	48	36	75
At operating voltage of 24 V				
Positioning time [ms]	30	62	44	100


## Positioning time $t$ as a function of effective load $m$ and voltage $U$




At  $U = 48\text{ V}$   
ADNE-32-15/35




At  $U = 24\text{ V}$   
ADNE-32-15/35



ADNE-40-20/45




ADNE-40-20/45



# Short-stroke cylinders ADNE-LAS, with linear motor


Technical data

## Min. positioning time $t$ as a function of voltage $U$ , at an effective load of 0 g




Size	32		40	
Stroke [mm]	15	35	20	45
At operating voltage of 48 V				
Positioning time [ms]	64	102	77	160
At operating voltage of 24 V				
Positioning time [ms]	64	132	94	213


## Positioning time $t$ as a function of effective load $m$ and voltage $U$




At  $U = 48\text{ V}$   
ADNE-32-15/35




At  $U = 24\text{ V}$   
ADNE-32-15/35



ADNE-40-20/45



ADNE-40-20/45




# Short-stroke cylinders ADNE-LAS, with linear motor

Technical data

FESTO

Dimensions – Basic version

Download CAD data → [www.festo.com](http://www.festo.com)



Size	Stroke [mm]	B1	B2	BG	D5 ∅ F9	E +0.3	G	H1	H2	LA +0.4
32	15	37	25	26	9	47	17.5	13	50	4.6
	35									
40	20									
	45					54.5				

Size	Stroke [mm]	LA1	L4	MM ∅ h9	RT	SF h13	TG ±0.2	ZA +0.4/-0.2	ZB +0.75/-0.35
32	15	5	9.1	8	M6	7	32.5	110.8	117.65
	35							150.8	157.65
40	20			10		9	38	136.5	143.4
	45							186.5	193.4


# Short-stroke cylinders ADNE-LAS, with linear motor

Technical data

## Dimensions – Variants

Download CAD data → [www.festo.com](http://www.festo.com)


A – Male thread



1 Hex nut DIN 439-B included in the scope of delivery

Size	Stroke [mm]	A -0.5	D7 ∅	D9 ∅	KK	L5	WH +0.75 -0.55	ZB +0.75 -0.35
32	15	12	4.5	3.2	M6	3	6.85	117.65
	35							157.65
40	20	16	6	3.8	M8	2	6.9	143.4
	45							193.4

## S20 – Through, hollow piston rod



1 Hex nut DIN 439-B included in the scope of delivery  
+ = plus stroke length

Size	Stroke [mm]	A -0.5	D7 ∅	D9 ∅	KK	L5	WH +0.75 -0.55	WH2 +0.55 -0.75	ZM +0.6 -0.4
32	15	12	4.5	3.2	M6	3	6.85	6.85	140
	35								200
40	20	16	6	3.8	M8	2	6.9	6.9	170.8
	45								245.8

# Short-stroke cylinders ADNE-LAS, with linear motor



Ordering data – Modular products

Ordering table					
Size	32	40	Condi- tions	Code	Enter code
<b>M</b> Module No.	<b>566415</b>	<b>566416</b>			
Function	Electric short-stroke cylinder, based on ISO 21287			<b>ADNE</b>	ADNE
Size	32	40		-...	
Stroke [mm]	15, 35	20, 45		-...	
Drive type	Linear motor			<b>-L</b>	-L
Motor technology	AC synchronous			<b>AS</b>	AS
Piston rod thread	Male thread			<b>-A</b>	A
<b>O</b> Type of piston rod	Through, hollow piston rod			<b>-S20</b>	


Transfer order code

# Short-stroke cylinders ADNE-LAS, with linear motor

Accessories

## Foot mounting HNA

Material:  
 HNA: Galvanised steel  
 HNA-...-R3: Steel with protective coating  
 Free of copper and PTFE  
 RoHS-compliant




Dimensions and ordering data										
For size	Stroke	AB ∅	AH	A0	AT	AU	SA	TR	US	XA
	[mm]	H14	JS14		±0.5	±0.2		±0.2	-0.5	
32	15	7	33.5	7	4	16	142.8	32	46	133.65
	35						182.8			173.65
40	20	10	38	9	4	18	172.5	36	54	161.4
	45						222.5			211.4

For size	Basic version			High corrosion protection		
	CRC <sup>1)</sup>	Weight [g]	Part No. Type	CRC <sup>1)</sup>	Weight [g]	Part No. Type
32	1	123	<b>537241 HNA-32</b>	3	123	<b>537256 HNA-32-R3</b>
40	1	157	<b>537242 HNA-40</b>	3	157	<b>537257 HNA-40-R3</b>

## Flange mounting FNC

Material:  
 Galvanised steel  
 Free of copper and PTFE  
 RoHS-compliant



Dimensions and ordering data								
For size	Stroke	E	FB ∅	MF	R	TF	UF	ZF
	[mm]						±1	
32	15	45	7	10	32	64	80	127.65
	35							167.65
40	20	54	9	10	36	72	90	153.4
	45							203.4

For size	Basic version			High corrosion protection		
	CRC <sup>1)</sup>	Weight [g]	Part No. Type	CRC <sup>1)</sup>	Weight [g]	Part No. Type
32	1	221	<b>174376 FNC-32</b>	4	220	<b>161846 CRFNG-32</b>
40	1	291	<b>174377 FNC-40</b>	4	291	<b>161847 CRFNG-40</b>

1) Corrosion resistance class CRC 1 to Festo standard FN 940070  
 Low corrosion stress. For dry indoor applications or transport and storage protection. Also applies to parts behind covers, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions).  
 Corrosion resistance class CRC 3 to Festo standard FN 940070  
 High corrosion stress. Outdoor exposure under moderate corrosive conditions. External visible parts with primarily functional requirements for the surface and which are in direct contact with a normal industrial environment.


Corrosion resistance class CRC 4 to Festo standard FN 940070  
 Particularly high corrosion stress. Outdoor exposure under extreme corrosive conditions. Parts exposed to aggressive media, for instance in the chemical or food industries. These applications may need to be supported by special tests (→ also FN 940082) using appropriate media.

# Short-stroke cylinders ADNE-LAS, with linear motor

Accessories

## Swivel flange SNCL

Material:  
 SNCL: Die-cast aluminium  
 Free of copper and PTFE  
 RoHS-compliant




Dimensions and ordering data							
For size	Stroke	CD	EW	FL	L	MR	XC
	[mm]	∅ H9	h12	±0.2			
32	15	10	26	22	13	10	139.65
	35						179.65
40	20	12	28	25	16	12	168.4
	45						218.4

For size	Basic version		Weight [g]	Part No.	Type
	CRC <sup>1)</sup>				
32	2		85	174404	SNCL-32
40	2		115	174405	SNCL-40

## Swivel flange SNCB/SNCB-...-R3

Material:  
 SNCB: Die-cast aluminium  
 SNCB-...-R3: Die-cast aluminium with protective coating, high corrosion protection  
 Free of copper and PTFE  
 RoHS-compliant



Dimensions and ordering data							
For size	Stroke	CB	EK	FL	L	MR	XC
	[mm]	H14	∅ e8	±0.2			
32	15	26	10	22	13	8.5	139.65
	35						179.65
40	20	28	12	25	16	12	168.4
	45						218.4

For size	Basic version			High corrosion protection		
	CRC <sup>1)</sup>	Weight [g]	Part No. Type	CRC <sup>1)</sup>	Weight [g]	Part No. Type
32	2	103	174390 SNCB-32	3	100	176944 SNCB-32-R3
40	2	155	174391 SNCB-40	3	151	176945 SNCB-40-R3

1) Corrosion resistance class 2 according to Festo standard 940 070  
 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.  
 Corrosion resistance class 3 according to Festo standard 940 070  
 Components subject to high corrosion stress. External visible parts in direct contact with industrial atmospheres or media such as solvents and cleaning agents, with a predominantly functional requirement for the surface.





# Short-stroke cylinders ADNE-LAS, with linear motor

Accessories

## Swivel flange SNCS

Material:  
 SNCL: Die-cast aluminium  
 Free of copper and PTFE  
 RoHS-compliant




### Dimensions and ordering data

For size	Stroke [mm]	CN ∅	E	EP ±0.2	EX	FL ±0.2	LT	MS	RA +1	TG	XC
32	15	10 <sup>+0.013</sup>	45 <sup>+0.2/-0.5</sup>	10.5	14	22	13	15 <sup>+0.5</sup>	14.5	32.5	139.65
	35										179.65
40	20	12 <sup>+0.015</sup>	54 <sup>-0.5</sup>	12	16	25	16	17 <sup>+0.5</sup>	17.5	38	168.4
	45										218.4

For size	Basic version CRC <sup>1)</sup>	Weight [g]	Part No.	Type
32	2	86	174397	SNCS-32
40	2	122	174398	SNCS-40

## Trunnion flange ZNCF/CRZNG

Material:  
 ZNCF: Stainless steel casting  
 CRZNG: Electropolished stainless steel casting  
 Free of copper and PTFE  
 RoHS-compliant



### Dimensions and ordering data








For size	Stroke [mm]	C2	C3	TD ∅ e9	TK	TL	TM	US	XH	XL
32	15	71	86	12	16	12	50	45	1.15	125.65
	35									165.65
40	20	87	105	16	20	16	63	54	3.1	153.4
	45									203.4






For size	Basic version				High corrosion protection			
	CRC <sup>1)</sup>	Weight [g]	Part No.	Type	CRC <sup>1)</sup>	Weight [g]	Part No.	Type
32	2	150	174411	ZNCF-32	4	150	161852	CRZNG-32
40	2	285	174412	ZNCF-40	4	285	161853	CRZNG-40

1) Corrosion resistance class 2 according to Festo standard 940 070  
 Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.  
 Corrosion resistance class 4 according to Festo standard 940 070  
 Components subject to particularly high corrosion stress. Parts used with aggressive media, e.g. in the food or chemical industry. These applications should be supported with special tests with the media if required.

# Short-stroke cylinders ADNE-LAS, with linear motor

Accessories

Ordering data			
Designation	For size	Part No.	Type
<b>Trunnion support LNZG</b>			
	32	32959	LNZG-32
	40	32960	LNZG-40/50
<b>Trunnion support CRLNZG, corrosion-resistant</b>			
	32	161874	CRLNZG-32
	40	161875	CRLNZG-40/50
<b>Clevis foot LNG</b>			
	32	33890	LNG-32
	40	33891	LNG-40
<b>Clevis foot CRLNG, corrosion-resistant</b>			
	32	161840	CRLNG-32
	40	161841	CRLNG-40
<b>Clevis foot LBG</b>			
	32	31761	LBG-32
	40	31762	LBG-40
<b>Rod eye SGS</b>			
	32	9254	SGS-M6
	40	9255	SGS-M8
<b>Rod eye CRSGS, corrosion-resistant</b>			
	32	195580	CRSGS-M6
	40	195581	CRSGS-M8

Ordering data			
Designation	For size	Part No.	Type
<b>Coupling piece KSZ</b>			
	32	36123	KSZ-M6
	40	36124	KSZ-M8
<b>Adapter AD</b>			
	32	157328	AD-M6-M5
		157329	AD-M6-1/8
		157330	AD-M6-1/4
	40	157331	AD-M8-1/8
		157332	AD-M8-1/4
<b>Rod clevis SG</b>			
	32	3110	SG-M6
	40	3111	SG-M8
<b>Rod clevis CRSG, corrosion-resistant</b>			
	32	13567	CRSG-M6
	40	13568	CRSG-M8
<b>Self-aligning rod coupler FK</b>			
	32	2061	FK-M6
	40	2062	FK-M8


## Product Range and Company Overview

### A Complete Suite and Company Overview

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



**Custom Automation Components**  
Complete custom engineered solutions



**Custom Control Cabinets**  
Comprehensive engineering support and on-site services



**Complete Systems**  
Shipment, stocking and storage services

### The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



**Electromechanical**  
Electromechanical actuators, motors, controllers & drivers



**Pneumatics**  
Pneumatic linear and rotary actuators, valves, and air supply



**PLCs and I/O Devices**  
PLC's, operator interfaces, sensors and I/O devices

### Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 16,000 employees in 60 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

### Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.




© Copyright 2013, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmental friendly printing plant.

# Festo North America



**1 Festo Canada  
Headquarters  
Festo Inc.**  
5300 Explorer Drive  
Mississauga, ON  
L4W 5G4

**2 Montréal**  
5600, Trans-Canada  
Pointe-Claire, QC  
H9R 1B6

**3 Québec City**  
2930, rue Watt#117  
Québec, QC  
G1X 4G3



**4 Festo United States  
Headquarters  
Festo Corporation**  
395 Moreland Road  
Hauppauge, NY  
11788

**5 Appleton**  
North 922 Tower View Drive, Suite N  
Greenville, WI  
54942

**7 Detroit**  
1441 West Long Lake Road  
Troy, MI  
48098

**6 Chicago**  
85 W Algonquin - Suite 340  
Arlington Heights, IL  
60005

**8 Silicon Valley**  
4935 Southfront Road, Suite F  
Livermore, CA  
94550

## Festo Regional Contact Center

### Canadian Customers

Commercial Support:  
Tel: 1 877 GO FESTO (1 877 463 3786)  
Fax: 1 877 FX FESTO (1 877 393 3786)  
Email: festo.canada@ca.festo.com

Technical Support:  
Tel: 1 866 GO FESTO (1 866 463 3786)  
Fax: 1 877 FX FESTO (1 877 393 3786)  
Email: technical.support@ca.festo.com

### USA Customers

Commercial Support:  
Tel: 1 800 99 FESTO (1 800 993 3786)  
Fax: 1 800 96 FESTO (1 800 963 3786)  
Email: customer.service@us.festo.com

Technical Support:  
Tel: 1 866 GO FESTO (1 866 463 3786)  
Fax: 1 800 96 FESTO (1 800 963 3786)  
Email: product.support@us.festo.com