

## Soft-start/quick exhaust valves MS-SV, MS series

**FESTO**



## Key features

### Service unit components of the MS series

Solutions for every application

With its large product range, highly effective components and a wide choice of functions, the MS series from Festo offers a complete concept for compressed air preparation. It is suitable for simple standard applications as well as application-specific solutions with very high quality requirements. Available as individual components, pre-assembled combinations ex-stock,

application-specific combinations or complete turnkey solutions. The five sizes in the MS series achieve maximum flow rates with low space requirements.

### Freely combinable function modules

Pressure regulators, on/off and soft-start valves with safety function, filters, pressure and flow sensors, dryers, sensors and lubricators can be assembled into a suitable solution for every task. With the modular structure the components can be combined as required. The simple connection system saves time because replacing individu-

al modules does not require disassembling the entire combination. Many of the components are also UL and ATEX certified.

### CAD models and configurator

Convenient tools for planning and selecting application-specific individual components and combinations. The product configurator can be used to configure customised solutions quickly and to transfer the order data without any hassle.

### Engineering tools

Selection tool for choosing the right service unit without oversizing, and with the right air purity class:

→ [www.festo.com/engineering/service-unit](http://www.festo.com/engineering/service-unit)

### Air quality

This program supports configuring an appropriate service unit. Please insert the required air cleanliness either by your application or an ISO-code or by direct selection of air filters.

**Selection criteria: Application**

Filter combination is proposed based upon your selected application

- standard pneumatics operation of valves and cylinders, e.g. in automotive industry, secondary packaging
- mining and building industry applications without special air cleanliness requirements
- application of pressure operated tools and machines pneumatic hammer, air engine, positioning with proportional valve
- electronic, flatpanel and solar industry, textile and paper production application with residual oil content <math>< 0.3 \text{ mg/m}^3</math>
- painting, powder coating, air bearing application with residual oil content <math>< 0.01 \text{ mg/m}^3</math>
- food and beverage industry, optics application with residual oil content <math>< 0.003 \text{ mg/m}^3</math> reduction of oil vapours and aromas

**Selection criteria: ISO-class**

Filter combination is proposed based upon the air cleanliness class according to ISO 8573-1:2010

particle : 4 \* :

**ISO**

\* Downstream from the compressor the water content is assumed to be ISO class 4. Better classes can be achieved by applying an adsorption dryer PDAD or a membrane dryer LDM1

**Direct filter selection**

Independent selection of filter combination

- 40 µm Filter
- 5 µm Filter
- 1 µm Fine Filter
- 0.01 µm Micro Filter \*
- Active Carbon Filter

\* To enhance the filter lifetime and in consequence the maintenance intervals arrange a 1 µm Fine Filter in front of the 0.01 µm Micro Filter as a preliminary filter.

### Integrated sensors

Pressure and flow sensors

### Safety functions

Soft-start/quick exhaust valves MS6-SV/MS9-SV

### Saving energy

Service unit combinations MSE6

Intelligent mix of sizes



- Maximum machine availability thanks to controlled processes
- Reliable compressed air preparation and system supply
- Integrated or stand-alone
- Easy to connect with M8/M12 plug

- Fast and reliable exhausting of systems up to Performance Level e, certified to EN ISO 13849-1
- Integrated soft-start function

- Fully automatic monitoring and regulation of the compressed air supply
- Automatic shut-off of the compressed air in standby mode
- Detection and notification of leakages
- Condition monitoring of relevant process data

- Optimum flow rate with a size that is up to 18% smaller
- Excellent energy efficiency
- Cost-optimised combinations – save up to 30%!

### Size differences

| Size  | MS2      | MS4              | MS6                    | MS9                            | MS12                   |
|---|----------|------------------|------------------------|--------------------------------|------------------------|
| Grid dimension [mm]                         | 25       | 40               | 62                     | 90                             | 124                    |
| Connection sizes                            | M5, QS-6 | G1/8, G1/4, G3/8 | G1/4, G3/8, G1/2, G3/4 | G1/2, G3/4, G1, G1 1/4, G1 1/2 | G1, G1 1/4, G1 1/2, G2 |
| Standard nominal flow rate $q_{N1}$ [l/min] | 350      | 1800             | 6500                   | 20000                          | 22000                  |

1) Using pressure regulator MS-LR as an example

## Key features

## Note

## Information

The next few pages provide a brief overview of the product range for the MS series service unit components.

You can find detailed information and all the technical data in the documentation for the relevant service unit component.

Accessories such as connecting plates or mounting brackets can be ordered either via the configurator or separately.

## Design of a service unit

The order of the individual service unit components within a combination is relevant for safety and functionality. The service unit components cannot be combined in any order in the flow direction. They are subject to restrictions and rules.





The configurator for the service unit MSB is a reliable and convenient way of arranging individual service unit components and it ensures compliance with the applicable rules. As a result, you get a fully assembled unit, including UL or ATEX certification, if necessary.

When combining a unit from individually configured and ordered service unit components, the points on the right must be adhered to under all circumstances.







- Regulators MS-LFR/LR/LRP/LRE are only permissible in the flow direction with the same or decreasing pressure regulation range
- Filters MS-LFR/LF/LFM/LFX are only permissible in the flow direction with an increasing grade of filtration
- Lubricators MS-LOE are not permitted in the flow direction upstream of a filter MS-LFR/LFM/LF/LFX, water separator MS-LWS or membrane air dryer MS-LDM1

- A micro filter MS-LFM must be installed in the flow direction upstream of an activated carbon filter MS-LFX or membrane air dryer MS-LDM1
- A flow sensor SFAM cannot be installed directly downstream of a regulator MS-LFR/LR; a branching module MS-FRM must be positioned between them
- A soft-start/quick exhaust valve MS-SV must be the last service unit component in the flow direction



## Product range for service unit components of the MS series

| Type  | Description   | Size | Pneumatic connection |               |               |        |                              |                             |
|---|---|------|----------------------|---------------|---------------|--------|------------------------------|-----------------------------|
|   |   |      | Push-in connector    | Female thread |               |        | Connecting plate with thread |                             |
|   |   |      |                      | M             | G             | NPT    | G                            | NPT                         |
| <b>Combinations</b>   |   |      |                      |               |               |        |                              |                             |
| <b>Service unit combinations MSB-FRC</b>  |   |      |                      |               |               |        |                              | Datasheets → Internet: msb  |
|  | Combinations of filter regulator and lubricator   | 4    | –                    | –             | 1/8, 1/4      | –      | –                            | –                           |
|   |   | 6    | –                    | –             | 1/4, 3/8, 1/2 | –      | –                            | –                           |
| <b>Service unit combinations MSB</b>  |   |      |                      |               |               |        |                              |                             |
| <b>Service unit combinations MSB</b>  |   |      |                      |               |               |        |                              | Datasheets → Internet: msb  |
|  | 7 combinations, predefined  | 4    | –                    | –             | 1/4           | –      | –                            | –                           |
|   |   | 6    | –                    | –             | 1/2           | –      | –                            | –                           |
|  | Freely configurable combinations  | 4    | –                    | –             | 1/8, 1/4      | –      | 1/8, 1/4, 3/8                | 1/8, 1/4, 3/8               |
|   |   | 6    | –                    | –             | 1/4, 3/8, 1/2 | –      | 1/4, 3/8, 1/2, 3/4           | 1/4, 3/8, 1/2, 3/4          |
|   |   | 9    | –                    | –             | 3/4, 1        | 3/4, 1 | 1/2, 3/4, 1, 1 1/4, 1 1/2    | 1/2, 3/4, 1, 1 1/4, 1 1/2   |
| <b>Service unit combinations MSE6</b>   |   |      |                      |               |               |        |                              |                             |
| <b>Service unit combinations MSE6</b>   |   |      |                      |               |               |        |                              | Datasheets → Internet: mse6 |
|  | Combinations with fieldbus connection for measuring pressure, flow rate and consumption | 6    | –                    | –             | –             | –      | 1/2                          | –                           |
|   |   |      |                      |               |               |        |                              |                             |






## Key features

| Product range for service unit components of the MS series                          |   |      |   |               |               |                              |                           |                           |
|---|---|------|---|---------------|---------------|------------------------------|---------------------------|---------------------------|
| Type  | Description   | Size | Pneumatic connection  |               |               | Connecting plate with thread |                           |                           |
|   |   |      | Push-in connector   | Female thread |               | G                            |                           | NPT                       |
|   |   |      | M   | G             | NPT           | G                            | NPT                       |                           |
| <b>Individual devices</b>   |   |      |   |               |               |                              |                           |                           |
| <b>Filter regulators MS-LFR</b>   |   |      | Datasheets → Internet: ms2-lfr; ms4-lfr; ms6-lfr; ms9-lfr; ms12-lfr |               |               |                              |                           |                           |
|    | Filter and pressure regulator in a single device, grade of filtration 5 or 40 µm                    | 2    | QS-6  | M5            | –             | –                            | –                         | –                         |
|   |   | 4    | –   | –             | 1/8, 1/4      | –                            | 1/8, 1/4, 3/8             | 1/8, 1/4, 3/8             |
|   |   | 6    | –   | –             | 1/4, 3/8, 1/2 | –                            | 1/4, 3/8, 1/2, 3/4        | 1/4, 3/8, 1/2, 3/4        |
|   |   | 9    | –   | –             | 3/4, 1        | 3/4, 1                       | 1/2, 3/4, 1, 1 1/4, 1 1/2 | 1/2, 3/4, 1, 1 1/4, 1 1/2 |
|   |   | 12   | –   | –             | –             | –                            | 1, 1 1/4, 1 1/2, 2        | –                         |
| <b>Filter regulators MS-LFR-B</b>   |   |      | Datasheets → Internet: ms4-lfr-b; ms6-lfr-b                         |               |               |                              |                           |                           |
|    | Filter and pressure regulator in a single device in polymer housing, grade of filtration 5 or 40 µm | 4    | –   | –             | 1/4           | –                            | –                         | –                         |
|   |   | 6    | –   | –             | 1/2           | –                            | –                         | –                         |
| <b>Filters MS-LF</b>  |   |      | Datasheets → Internet: ms4-lf; ms6-lf; ms9-lf; ms12-lf              |               |               |                              |                           |                           |
|    | Grade of filtration 5 or 40 µm  | 4    | –   | –             | 1/8, 1/4      | –                            | 1/8, 1/4, 3/8             | 1/8, 1/4, 3/8             |
|   |   | 6    | –   | –             | 1/4, 3/8, 1/2 | –                            | 1/4, 3/8, 1/2, 3/4        | 1/4, 3/8, 1/2, 3/4        |
|   |   | 9    | –   | –             | 3/4, 1        | 3/4, 1                       | 1/2, 3/4, 1, 1 1/4, 1 1/2 | 1/2, 3/4, 1, 1 1/4, 1 1/2 |
|   |   | 12   | –   | –             | –             | –                            | 1, 1 1/4, 1 1/2, 2        | –                         |
| <b>Fine and micro filters MS-LFM</b>  |   |      | Datasheets → Internet: ms4-lfm; ms6-lfm; ms9-lfm; ms12-lfm          |               |               |                              |                           |                           |
|  | Grade of filtration 0.01 or 1 µm  | 4    | –   | –             | 1/8, 1/4      | –                            | 1/8, 1/4, 3/8             | 1/8, 1/4, 3/8             |
|   |   | 6    | –   | –             | 1/4, 3/8, 1/2 | –                            | 1/4, 3/8, 1/2, 3/4        | 1/4, 3/8, 1/2, 3/4        |
|   |   | 9    | –   | –             | 3/4, 1        | 3/4, 1                       | 1/2, 3/4, 1, 1 1/4, 1 1/2 | 1/2, 3/4, 1, 1 1/4, 1 1/2 |
|   |   | 12   | –   | –             | –             | –                            | 1, 1 1/4, 1 1/2, 2        | –                         |
| <b>Activated carbon filters MS-LFX</b>  |   |      | Datasheets → Internet: ms4-lfx; ms6-lfx; ms9-lfx; ms12-lfx          |               |               |                              |                           |                           |
|  | For removing liquid and gaseous oil particles   | 4    | –   | –             | 1/8, 1/4      | –                            | 1/8, 1/4, 3/8             | 1/8, 1/4, 3/8             |
|   |   | 6    | –   | –             | 1/4, 3/8, 1/2 | –                            | 1/4, 3/8, 1/2, 3/4        | 1/4, 3/8, 1/2, 3/4        |
|   |   | 9    | –   | –             | 3/4, 1        | 3/4, 1                       | 1/2, 3/4, 1, 1 1/4, 1 1/2 | 1/2, 3/4, 1, 1 1/4, 1 1/2 |
|   |   | 12   | –   | –             | –             | –                            | 1, 1 1/4, 1 1/2, 2        | –                         |
| <b>Water separators MS-LWS</b>  |   |      | Datasheets → Internet: ms6-lws; ms9-lws; ms12-lws                   |               |               |                              |                           |                           |
|  | Remove condensate from compressed air, maintenance-free   | 6    | –   | –             | 1/4, 3/8, 1/2 | –                            | 1/4, 3/8, 1/2, 3/4        | 1/4, 3/8, 1/2, 3/4        |
|   |   | 9    | –   | –             | 3/4, 1        | 3/4, 1                       | 1/2, 3/4, 1, 1 1/4, 1 1/2 | 1/2, 3/4, 1, 1 1/4, 1 1/2 |
|   |   | 12   | –   | –             | –             | –                            | 1, 1 1/4, 1 1/2, 2        | –                         |





## Key features

| Product range for service unit components of the MS series   |   |      |                      |               |               |        |                              |                           |
|--|---|------|----------------------|---------------|---------------|--------|------------------------------|---------------------------|
| Type   | Description   | Size | Pneumatic connection |               |               |        |                              |                           |
|  |   |      | Push-in connector    | Female thread |               |        | Connecting plate with thread |                           |
|  |   |      |                      | M             | G             | NPT    | G                            | NPT                       |
| <b>Individual devices</b>  |   |      |                      |               |               |        |                              |                           |
| <b>Pressure regulators MS-LR</b> <span style="float: right;">Datasheets → Internet: ms2-lr; ms4-lr; ms6-lr; ms9-lr; ms12-lr</span> |   |      |                      |               |               |        |                              |                           |
|   | For setting the required operating pressure, 4 pressure regulation ranges   | 2    | QS-6                 | M5            | –             | –      | –                            | –                         |
|  |   | 4    | –                    | –             | 1/8, 1/4      | –      | 1/8, 1/4, 3/8                | 1/8, 1/4, 3/8             |
|  |   | 6    | –                    | –             | 1/4, 3/8, 1/2 | –      | 1/4, 3/8, 1/2, 3/4           | 1/4, 3/8, 1/2, 3/4        |
|  |   | 9    | –                    | –             | 3/4, 1        | 3/4, 1 | 1/2, 3/4, 1, 1 1/4, 1 1/2    | 1/2, 3/4, 1, 1 1/4, 1 1/2 |
|  |   | 12   | –                    | –             | –             | –      | 1, 1 1/4, 1 1/2, 2           | –                         |
| <b>Pressure regulators MS-LR-B</b> <span style="float: right;">Datasheets → Internet: ms4-lr-b; ms6-lr-b</span>                    |   |      |                      |               |               |        |                              |                           |
|   | For setting the required operating pressure, in polymer housing   | 4    | –                    | –             | 1/4           | –      | –                            | –                         |
|  |   | 6    | –                    | –             | 1/2           | –      | –                            | –                         |
| <b>Pressure regulators MS-LRB</b> <span style="float: right;">Datasheets → Internet: ms4-lrb; ms6-lrb</span>                       |   |      |                      |               |               |        |                              |                           |
|   | For configuring a regulator manifold with independent pressure regulation ranges. Pressure output is to the front or rear.              | 4    | –                    | –             | 1/4           | –      | 1/8, 1/4, 3/8                | –                         |
|  |   | 6    | –                    | –             | 1/2           | –      | 1/4, 3/8, 1/2, 3/4           | –                         |
| <b>Precision pressure regulators MS-LRP</b> <span style="float: right;">Datasheets → Internet: ms6-lrp</span>                      |   |      |                      |               |               |        |                              |                           |
|   | For the precise setting of the required operating pressure, 4 pressure regulation ranges, pressure hysteresis 0.02 bar                  | 6    | –                    | –             | 1/4, 3/8, 1/2 | –      | 1/4, 3/8, 1/2, 3/4           | 1/4, 3/8, 1/2, 3/4        |
|  |   |      |                      |               |               |        |                              |                           |
| <b>Precision pressure regulators MS-LRPB</b> <span style="float: right;">Datasheets → Internet: ms6-lrpb</span>                    |   |      |                      |               |               |        |                              |                           |
|   | For configuring a regulator manifold with independent pressure regulation ranges. Pressure output is to the front or rear.              | 6    | –                    | –             | 1/2           | –      | 1/4, 3/8, 1/2, 3/4           | –                         |
|  |   |      |                      |               |               |        |                              |                           |
| <b>Electric pressure regulators MS-LRE</b> <span style="float: right;">Datasheets → Internet: ms6-lre</span>                       |   |      |                      |               |               |        |                              |                           |
|   | Electrically adjustable pressure regulator, 4 pressure regulation ranges  | 6    | –                    | –             | 1/4, 3/8, 1/2 | –      | 1/4, 3/8, 1/2, 3/4           | 1/4, 3/8, 1/2, 3/4        |
|  |   |      |                      |               |               |        |                              |                           |
| <b>Lubricators MS-LOE</b> <span style="float: right;">Datasheets → Internet: ms4-loe; ms6-loe; ms9-loe; ms12-loe</span>            |   |      |                      |               |               |        |                              |                           |
|   | Add a precisely adjustable amount of oil to the compressed air. The amount of oil mist is proportional to the compressed air flow rate. | 4    | –                    | –             | 1/8, 1/4      | –      | 1/8, 1/4, 3/8                | 1/8, 1/4, 3/8             |
|  |   | 6    | –                    | –             | 1/4, 3/8, 1/2 | –      | 1/4, 3/8, 1/2, 3/4           | 1/4, 3/8, 1/2, 3/4        |
|  |   | 9    | –                    | –             | 3/4, 1        | 3/4, 1 | 1/2, 3/4, 1, 1 1/4, 1 1/2    | 1/2, 3/4, 1, 1 1/4, 1 1/2 |
|  |   | 12   | –                    | –             | –             | –      | 1, 1 1/4, 1 1/2, 2           | –                         |

## Key features

| Product range for service unit components of the MS series                          |   |      |                      |               |               |  |                           |                           |
|---|---|------|----------------------|---------------|---------------|--|---------------------------|---------------------------|
| Type  | Description   | Size | Pneumatic connection |               |               | Connecting plate with thread                           |                           |                           |
|   |   |      | Push-in connector    | Female thread |               | G  |                           | NPT                       |
|   |   |      | M                    | G             | NPT           | G  | NPT                       |                           |
| <b>Individual devices</b>   |   |      |                      |               |               |  |                           |                           |
| <b>On/off valves MS-EM</b>  |   |      |                      |               |               | Datasheets → Internet: ms4-em; ms6-em; ms9-em; ms12-em |                           |                           |
|    | Manually actuated on/off valve for pressurising and exhausting pneumatic systems.   | 4    | –                    | –             | 1/8, 1/4      | –  | 1/8, 1/4, 3/8             | 1/8, 1/4, 3/8             |
|   |   | 6    | –                    | –             | 1/4, 3/8, 1/2 | –  | 1/4, 3/8, 1/2, 3/4        | 1/4, 3/8, 1/2, 3/4        |
|   |   | 9    | –                    | –             | 3/4, 1        | 3/4, 1   | 1/2, 3/4, 1, 1 1/4, 1 1/2 | 1/2, 3/4, 1, 1 1/4, 1 1/2 |
|   |   | 12   | –                    | –             | –             | –  | 1, 1 1/4, 1 1/2, 2        | –                         |
| <b>On/off valves MS-EE</b>  |   |      |                      |               |               |  |                           |                           |
| <b>On/off valves MS-EE</b>  |   |      |                      |               |               | Datasheets → Internet: ms4-ee; ms6-ee; ms9-ee; ms12-ee |                           |                           |
|    | Electrically actuated on/off valve for pressurising and exhausting pneumatic systems.   | 4    | –                    | –             | 1/8, 1/4      | –  | 1/8, 1/4, 3/8             | 1/8, 1/4, 3/8             |
|   |   | 6    | –                    | –             | 1/4, 3/8, 1/2 | –  | 1/4, 3/8, 1/2, 3/4        | 1/4, 3/8, 1/2, 3/4        |
|   |   | 9    | –                    | –             | 3/4, 1        | 3/4, 1   | 1/2, 3/4, 1, 1 1/4, 1 1/2 | 1/2, 3/4, 1, 1 1/4, 1 1/2 |
|   |   | 12   | –                    | –             | –             | –  | 1, 1 1/4, 1 1/2, 2        | –                         |
| <b>On/off valves MS-EE-B</b>  |   |      |                      |               |               |  |                           |                           |
| <b>On/off valves MS-EE-B</b>  |   |      |                      |               |               | Datasheets → Internet: ms4-ee-b; ms6-ee-b              |                           |                           |
|    | Electrically actuated on/off valve in polymer housing for pressurising and exhausting pneumatic systems.                        | 4    | –                    | –             | 1/4           | –  | –                         | –                         |
|   |   | 6    | –                    | –             | 1/2           | –  | –                         | –                         |
| <b>Soft-start valves MS-DL</b>  |   |      |                      |               |               |  |                           |                           |
| <b>Soft-start valves MS-DL</b>  |   |      |                      |               |               | Datasheets → Internet: ms4-dl; ms6-dl; ms12-dl         |                           |                           |
|  | Pneumatically actuated soft-start valve for slow pressurisation and exhaust of pneumatic installations.                         | 4    | –                    | –             | 1/8, 1/4      | –  | 1/8, 1/4, 3/8             | 1/8, 1/4, 3/8             |
|   |   | 6    | –                    | –             | 1/4, 3/8, 1/2 | –  | 1/4, 3/8, 1/2, 3/4        | 1/4, 3/8, 1/2, 3/4        |
|   |   | 12   | –                    | –             | –             | –  | 1, 1 1/4, 1 1/2, 2        | –                         |
| <b>Soft-start valves MS-DE</b>  |   |      |                      |               |               |  |                           |                           |
| <b>Soft-start valves MS-DE</b>  |   |      |                      |               |               | Datasheets → Internet: ms4-de; ms6-de; ms12-de         |                           |                           |
|  | Electrically actuated soft-start valve for slowly pressurising and exhausting pneumatic installations.                          | 4    | –                    | –             | 1/8, 1/4      | –  | 1/8, 1/4, 3/8             | 1/8, 1/4, 3/8             |
|   |   | 6    | –                    | –             | 1/4, 3/8, 1/2 | –  | 1/4, 3/8, 1/2, 3/4        | 1/4, 3/8, 1/2, 3/4        |
|   |   | 12   | –                    | –             | –             | –  | 1, 1 1/4, 1 1/2, 2        | –                         |
| <b>On/off valves MS-EDE-B</b>   |   |      |                      |               |               |  |                           |                           |
| <b>On/off valves MS-EDE-B</b>   |   |      |                      |               |               | Datasheets → Internet: ms4-ed-e-b; ms6-ed-e-b          |                           |                           |
|  | Electrically actuated soft-start valve in polymer housing for slowly pressurising and exhausting pneumatic installations.       | 4    | –                    | –             | 1/4           | –  | –                         | –                         |
|   |   | 6    | –                    | –             | 1/2           | –  | –                         | –                         |
| <b>Soft-start/quick exhaust valves MS-SV</b>  |   |      |                      |               |               |  |                           |                           |
| <b>Soft-start/quick exhaust valves MS-SV</b>  |   |      |                      |               |               | Datasheets → Internet: ms6-sv; ms9-sv                  |                           |                           |
|  | For gradually increasing pressurisation and quick, safe pressure reduction in pneumatic piping systems. Up to category 1, PL c. | 6    | –                    | –             | 1/2           | –  | 1/4, 3/8, 1/2, 3/4        | 1/4, 3/8, 1/2, 3/4        |
|   |   | 9    | –                    | –             | 3/4, 1        | 3/4, 1   | 1/2, 3/4, 1, 1 1/4, 1 1/2 | 1/2, 3/4, 1, 1 1/4, 1 1/2 |
|  | Up to category 3, PL d. Up to category 4, PL e in the case of optional extension.   | 6    | –                    | –             | 1/2           | –  | 1/4, 3/8, 1/2, 3/4        | 1/4, 3/8, 1/2, 3/4        |
|   |   |      |                      |               |               |  |                           |                           |
|  | Up to category 4, PL e.   | 6    | –                    | –             | 1/2           | –  | 1/4, 3/8, 1/2, 3/4        | –                         |
|   |   |      |                      |               |               |  |                           |                           |

## Key features

| Product range for service unit components of the MS series  |   |      |                      |               |               |        |                              |                           |
|---|---|------|----------------------|---------------|---------------|--------|------------------------------|---------------------------|
| Type  | Description   | Size | Pneumatic connection |               |               |        |                              |                           |
|   |   |      | Push-in connector    | Female thread |               |        | Connecting plate with thread |                           |
|   |   |      |                      | M             | G             | NPT    | G                            | NPT                       |
| <b>Individual devices</b>   |   |      |                      |               |               |        |                              |                           |
| <b>Membrane air dryers MS-LDM1</b> <span style="float: right;">Datasheets → Internet: ms4-ldm; ms6-ldm</span>                 |   |      |                      |               |               |        |                              |                           |
|    | Wear-free membrane dryer with internal air consumption                        | 4    | –                    | –             | 1/8, 1/4      | –      | 1/8, 1/4, 3/8                | 1/8, 1/4, 3/8             |
|   |   | 6    | –                    | –             | 1/4, 3/8, 1/2 | –      | 1/4, 3/8, 1/2, 3/4           | 1/4, 3/8, 1/2, 3/4        |
| <b>Branching modules MS-FRM</b> <span style="float: right;">Datasheets → Internet: ms4-frm; ms6-frm; ms9-frm; ms12-frm</span> |   |      |                      |               |               |        |                              |                           |
|    | Compressed air distributors with 4 connections                                | 4    | –                    | –             | 1/8, 1/4      | –      | 1/8, 1/4, 3/8                | –                         |
|   |   | 6    | –                    | –             | 1/4, 3/8, 1/2 | –      | 1/4, 3/8, 1/2, 3/4           | –                         |
|   |   | 9    | –                    | –             | 3/4, 1        | 3/4, 1 | 1/2, 3/4, 1, 1 1/4, 1 1/2    | 1/2, 3/4, 1, 1 1/4, 1 1/2 |
|   |   | 12   | –                    | –             | –             | –      | 1, 1 1/4, 1 1/2, 2           | –                         |
| <b>Distributor blocks MS-FRM-FRZ</b> <span style="float: right;">Datasheets → Internet: ms4-frm-frz; ms6-frm-frz</span>       |   |      |                      |               |               |        |                              |                           |
|    | Compressed air distributors with 4 connections and half the grid width        | 4    | –                    | –             | –             | –      | –                            | –                         |
|   |   | 6    | –                    | –             | –             | –      | –                            | –                         |
| <b>Flow sensors SFAM</b> <span style="float: right;">Datasheets → Internet: sfam</span>                                       |   |      |                      |               |               |        |                              |                           |
|    | For absolute flow rate information and cumulative air consumption measurement | 6    | –                    | –             | –             | –      | 1/2                          | 1/2                       |
|   |   | 9    | –                    | –             | –             | –      | 1, 1 1/2                     | 1, 1 1/2                  |

## Type codes MS6-SV

|            |               |
|------------|---------------|
| <b>001</b> | <b>Series</b> |
| <b>MS</b>  | MS series     |

|            |                      |
|------------|----------------------|
| <b>002</b> | <b>Size</b>          |
| <b>6</b>   | Grid dimension 62 mm |

|            |                                |
|------------|--------------------------------|
| <b>003</b> | <b>Function</b>                |
| <b>SV</b>  | Soft-start/quick exhaust valve |

|            |                             |
|------------|-----------------------------|
| <b>004</b> | <b>Pneumatic connection</b> |
| <b>1/2</b> | Female thread G1/2          |
| <b>AGB</b> | Sub-base G1/4               |
| <b>AGC</b> | Sub-base G3/8               |
| <b>AGD</b> | Sub-base G1/2               |
| <b>AGE</b> | Sub-base G3/4               |
| <b>AQN</b> | Sub-base 1/4 NPT            |
| <b>AQP</b> | Sub-base 3/8 NPT            |
| <b>AQR</b> | Sub-base 1/2 NPT            |
| <b>AQS</b> | Sub-base 3/4 NPT            |

|            |   |
|------------|---|
| <b>005</b> | <b>Performance Level</b>                                  |
| <b>C</b>   | Category 1, 1-channel to ISO 13849-1                      |
| <b>D</b>   | Category 3, 1-channel to ISO 13849-1                      |
| <b>E</b>   | Category 4, 2-channel with self-monitoring to ISO 13849-1 |

|               |  |
|---------------|--|
| <b>006</b>    | <b>Supply voltage</b>  |
| <b>10V24P</b> | 24 V DC, 10 bar, M12 plug socket adapter (connection pattern to EN 60947-5-2)  |
| <b>10V24</b>  | 24 V DC, 10 bar, connection pattern to EN 175301   |
| <b>10V24C</b> | 24 V DC, 10 bar (connection pattern to EN 175301) without manual override  |
| <b>10V24D</b> | 24 V DC, 10 bar, M12 (connection pattern to EN 60947-5-2) without manual override  |
| <b>10V24E</b> | 24 V DC, 10 bar, M12 (connection pattern to EN 60947-5-2) without manual override on the pilot actuator. With detenting internal manual override (can only be reset via 24 V). |
| <b>10V24F</b> | 24 V DC, 10 bar, M12 (connection pattern to EN 60947-5-2). Manual override on the pilot actuator non-detenting, internally detenting   |
| <b>ASIS</b>   | 22 V - 31.6 V DC, AS-i Safety at Work, SPEC3.0 Profile 7.5.5   |

|             |                                     |
|-------------|-------------------------------------|
| <b>007</b>  | <b>Connection technology</b>        |
|             | None                                |
| <b>20E</b>  | 2 SMT proximity sensors, 5 m, OE    |
| <b>2M8</b>  | 2 SMT proximity sensors, 0.3 m, M8  |
| <b>2M12</b> | 2 SMT proximity sensors, 0.3 m, M12 |

|            |   |
|------------|---|
| <b>008</b> | <b>Extended sensing</b>   |
|            | None  |
| <b>S3</b>  | Additional SMT proximity sensor; required to achieve Performance Level "e"; corresponds to the selected connection technology |

|            |                 |
|------------|-----------------|
| <b>009</b> | <b>Silencer</b> |
|            | None            |
| <b>S</b>   | Silencer        |
| <b>SO</b>  | Open silencer   |

|             |   |
|-------------|---|
| <b>010</b>  | <b>Pressure gauge alternatives</b>  |
|             | None  |
| <b>AG</b>   | MS pressure gauge   |
| <b>A8</b>   | Adapter for EN pressure gauge 1/8, without pressure gauge   |
| <b>A4</b>   | Adapter for EN pressure gauge 1/4, without pressure gauge   |
| <b>RG</b>   | Integrated pressure gauge, red/green scale  |
| <b>AD1</b>  | Pressure sensor with LCD display, M8 plug, PNP, 3-pin   |
| <b>AD2</b>  | Pressure sensor with LCD display, M8 plug, NPN, 3-pin   |
| <b>AD3</b>  | Pressure sensor with LCD display, M12 plug, PNP, 4-pin, analogue output 4 ... 20 mA                 |
| <b>AD4</b>  | Pressure sensor with LCD display, M12 plug, NPN, 4-pin, analogue output 4 ... 20 mA                 |
| <b>AD7</b>  | Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/O               |
| <b>AD8</b>  | Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/C               |
| <b>AD9</b>  | Pressure sensor with switching display, M8 plug, window comparator, PNP, N/O                        |
| <b>AD10</b> | Pressure sensor with operational status indicator, M8 plug, window comparator, PNP, N/C             |
| <b>AD11</b> | Pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA |
| <b>AD12</b> | Pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA  |

|            |   |
|------------|---|
| <b>011</b> | <b>Alternative pressure gauge scale</b> |
|            | MS pressure gauge                       |
| <b>PSI</b> | psi                                     |
| <b>MPA</b> | MPa                                     |

|            |   |
|------------|---|
| <b>012</b> | <b>Multi-pin plug socket</b>  |
|            | None  |
| <b>MP1</b> | Multi-pin plug socket, Sub-D, 9-pin, screw terminal, without cable, static enable signals (EN1 = 24 V, EN2 = 24 V)  |
| <b>MP3</b> | Multi-pin plug socket, Sub-D, 9-pin, screw terminal, without cable, static enable signals (EN1 = 0 V, EN2 = 24 V), cross-circuit detection possible                             |
| <b>MP5</b> | Multi-pin plug socket, Sub-D, 9-pin, screw terminal, without cable, enable signals static (EN1=0 V, EN2=24 V), galvanic isolation of the enable signals from the supply voltage |

|            |   |
|------------|---|
| <b>013</b> | <b>Type of mounting</b>   |
|            | Without mounting bracket  |
| <b>WP</b>  | Mounting bracket basic design   |
| <b>WPB</b> | Mounting bracket for large wall gap   |
| <b>WPM</b> | Mounting bracket for hooking in service unit components                                   |
| <b>WB</b>  | Mounting centrally at rear (wall mounting top and bottom), connecting plates not required |


|            |                          |
|------------|--------------------------|
| <b>014</b> | <b>Tamper protection</b> |
|            | None                     |
| <b>MK</b>  | Full                     |

|            |  |
|------------|--|
| <b>015</b> | <b>UL certification</b>                    |
|            | None                                       |
| <b>UL1</b> | cULus ordinary location for Canada and USA |

|            |                                   |
|------------|-----------------------------------|
| <b>016</b> | <b>Flow direction</b>             |
|            | Flow direction from left to right |
| <b>Z</b>   | Flow direction from right to left |



## Peripherals overview MS6-SV-C



## Mounting attachments and accessories



|      |                                   |   | Single device               |                          | Combination                 |                          | → Page/<br>Internet |
|------|-----------------------------------|---|-----------------------------|--------------------------|-----------------------------|--------------------------|---------------------|
|      |                                   |   | Without connecting<br>plate | With connecting<br>plate | Without connecting<br>plate | With connecting<br>plate |                     |
| [1]  | MS6-SV-C                          | Soft-start/quick exhaust<br>valve             | ■                           | ■                        | ■                           | ■                        | 9                   |
| [2]  | MS6-MV                            | Module connector                              | –                           | ■                        | ■                           | ■                        | ms6-mv              |
| [3]  | MS6-WP, MS6-WPB, MS6-WPE, MS6-WPM | Mounting bracket                              | ■                           | ■                        | ■                           | ■                        | ms6-wp              |
| [4]  | MS6-WB                            | Mounting bracket                              | ■                           | ■                        | –                           | –                        | ms6-wb              |
| [5]  | MS6-SV-C-MK                       | Covering                                      | ■                           | ■                        | ■                           | ■                        | 9                   |
| [6]  | MS6-END                           | Cover cap                                     | –                           | –                        | ■                           | –                        | ms6-end             |
| [7]  | MS6-AEND                          | Mounting plate                                | ■ <sup>1)</sup>             | –                        | ■ <sup>1)</sup>             | –                        | ms6-aend            |
| [8]  | MS6-AG...                         | Connecting plate SET                          | –                           | ■ <sup>1)</sup>          | –                           | ■ <sup>1)</sup>          | ms6-ag              |
|      | MS6-AQ...                         | Connecting plate SET                          | –                           | ■ <sup>1)</sup>          | –                           | ■ <sup>1)</sup>          | ms6-aq              |
| [9]  | NEBU-M8...-LE3, NEBU-M12...-LE4   | Connecting cable                              | ■                           | ■                        | ■                           | ■                        | 9                   |
| [10] | AD1 ... AD4                       | Pressure sensor SDE1 with<br>LCD display      | ■                           | ■                        | ■                           | ■                        | 9                   |
| [11] | AD11 ... AD12                     | Pressure sensor SPAU with<br>LCD display      | ■                           | ■                        | ■                           | ■                        | 9                   |
| [12] | NEBU-M8...-LE4/NEBU-M12...-LE4    | Connecting cable                              | ■                           | ■                        | ■                           | ■                        | 9                   |
| [13] | AD7 ... AD10                      | Pressure sensor SDE5 with<br>status indicator | ■                           | ■                        | ■                           | ■                        | 9                   |
| [14] | NEBU-M8...-LE3                    | Connecting cable                              | ■                           | ■                        | ■                           | ■                        | 9                   |
| [15] | A4                                | Adapter for EN pressure<br>gauge 1/4          | ■                           | ■                        | ■                           | ■                        | 9                   |
| [16] | MA                                | Pressure gauge                                | ■                           | ■                        | ■                           | ■                        | 9                   |
| [17] | AG, RG                            | MS pressure gauge                             | ■                           | ■                        | ■                           | ■                        | 9                   |
| [18] | U-3/4-B                           | Silencer                                      | ■                           | ■                        | ■                           | ■                        | 9                   |

1) Module connector MS6-MV [2] or mounting bracket MS6-WP, MS6-WPB, MS6-WPE, MS6-WPM [3] is required for mounting.

## Peripherals overview MS6-SV-C

Supply voltage  
Code: 10V24, 10V24C

Supply voltage  
Code: 10V24D, 10V24E, 10V24F,  
10V24P



**Note**

Additional accessories:


- Module connector for combination with size MS4, MS6 or size MS9  
→ Internet: amv rmv
- Adapter for mounting on profiles  
→ Internet: ipm





### Mounting attachments and accessories

|     |            |                        | Single device            |                       | Combination              |                       | → Page/<br>Internet |
|-----|------------|------------------------|--------------------------|-----------------------|--------------------------|-----------------------|---------------------|
|     |            |                        | Without connecting plate | With connecting plate | Without connecting plate | With connecting plate |                     |
| [1] | MEB-LD     | Illuminating seal      | ■                        | ■                     | ■                        | ■                     | 10                  |
| [2] | KMEB       | Plug socket with cable | ■                        | ■                     | ■                        | ■                     | 10                  |
| [3] | MSSD-EB    | Plug socket            | ■                        | ■                     | ■                        | ■                     | 10                  |
| [4] | NEBU-M12G5 | Connecting cable       | ■                        | ■                     | ■                        | ■                     | 10                  |
| [5] | NEBU-M12W5 | Connecting cable       | ■                        | ■                     | ■                        | ■                     | 10                  |

## Datasheet MS6-SV-C


MS6-SV...-10V24, 10V24F, 10V24P



-  - Flow rate  
5700 l/min
-  - Temperature range  
0 ... +60°C
-  - Operating pressure  
3 ... 10 bar
-  - [www.festo.com](http://www.festo.com)




MS6-SV...-10V24C, 10V24D



Electropneumatic soft-start/quick exhaust valve for gradual pressurisation and quick exhaust of system components (single channel).  
The main flow control valve in the cover permits a slow build-up of the output pressure p2. Once the output pressure p2 has reached the set pressure switchover point (switching pressure), the valve opens and the full operating pressure p1 is available at the output

- Suitable for applications with a high flow rate in restricted spaces with medium safety requirements up to controller category 1, Performance Level c
- High volumetric flow rate for pressurisation and exhaust
- The filling flow rate can be set for gradual pressure build-up using a flow control valve
- Adjustable pressure switchover point
- Optional pressure sensor
- Optional cover for the control sections as tamper protection

MS6-SV...-10V24E



## Safety data

|  |  |
|--|--|
| Conforms to  | EN ISO 13849-1   |
| Safety function  | Exhausting<br>Avoidance of unexpected start-up (pressurisation)  |
| Performance Level (PL)                                   | Exhausting: up to category 1, PL c<br>Prevention of unexpected start-up (pressurisation): up to category 1, PL c |
| Note on forced checking procedure                        | Switching frequency min. 1/month   |
| CE marking (see declaration of conformity) <sup>1)</sup> | To EU Machinery Directive  |
| Shock resistance   | Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27                                |
| Vibration resistance                                     | Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6                                 |

1) Additional information: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/...) → Support/Downloads.

## Note

The mechanical system is not tested in the controlled (i.e. pressurised) state.

Forced switch on/off: switching frequency should be at least once a month.

If the process-related switching frequency (safe exhausting) is less than once a month,

the machine operator must carry out a forced switch off.

## Datasheet MS6-SV-C

| General technical data    |   |
|---------------------------|---|
| Pneumatic connection 1, 2 |   |
| Female thread             | G1/2  |
| Connecting plate AG...    | G1/4, G3/8, G1/2 or G3/4  |
| Connecting plate AQ...    | 1/4 NPT, 3/8 NPT, 1/2 NPT or 3/4 NPT  |
| Pneumatic connection 3    | G3/4  |
| Actuation type            | Electrical  |
| Design                    | Piston spool  |
| Type of mounting          | Via accessories<br>In-line installation   |
| Mounting position         | Any   |
| Pressure indicator        | Via pressure sensor for indicating the output pressure and electrical output via LCD display<br>Via pressure sensor for indicating the output pressure and electrical output via switching status indicator<br>Via pressure gauge for displaying the output pressure<br>Via pressure gauge with red/green scale for indicating the output pressure<br>Prepared for G1/4 |
| Valve function            | 3/2-way valve, closed, single solenoid<br>Soft-start function, adjustable   |
| Non-overlapping           | Yes   |
| Exhaust air function      | Cannot be throttled   |
| Manual override           | 10V24, 10V24F<br>At the pilot solenoid valve: non-detenting<br>At the soft-start/quick exhaust valve: detenting, self-resetting   |
|                           | 10V24E<br>At the pilot solenoid valve: none<br>At the soft-start/quick exhaust valve: detenting, self-resetting   |
|                           | 10V24P<br>At the pilot solenoid valve: non-detenting/detenting<br>At the soft-start/quick exhaust valve: detenting, self-resetting  |
|                           | 10V24C, 10V24D<br>None  |
| Reset method              | Mechanical spring   |
| Type of control           | Piloted   |
| Pilot air supply          | Internal  |
| Sealing principle         | Soft  |

† Note: this product conforms to ISO 1179-1 and ISO 228-1.

| Characteristic flow rate values  |                    |
|--|--------------------|
| Pneumatic connection   | Female thread G1/2 |
| <b>Standard nominal flow rate <math>q_{nN}^{1)}</math> [l/min]</b>           |                    |
| In main flow direction 1 → 2   | 5700               |
| <b>Standard flow rate <math>q_N</math> [l/min], <math>p_2 = 6</math> bar</b> |                    |
| In exhaust direction 2 → 3   | 7600 <sup>2)</sup> |
| <b>C value [l/s*min]</b>   |                    |
| In main flow direction 1 → 2   | 23.2               |
| <b>b value</b>   |                    |
| In main flow direction 1 → 2   | 0.4                |

1) Measured at  $p_1 = 6$  bar and  $p_2 = 5$  bar,  $\Delta p = 1$  bar

2) Measured with reference to atmosphere with silencer S.

## Datasheet MS6-SV-C

| Electrical data          |                                   |  |
|--------------------------|-----------------------------------|--|
| Characteristic coil data | 10V24, 10V24P                     | 24 V DC: 1.8 W; permissible voltage fluctuations -10%/+10% |
|                          | 10V24C, 10V24D,<br>10V24E, 10V24F | 24 V DC: 1.8 W; permissible voltage fluctuations -15%/+10% |
| Electrical connection    | 10V24, 10V24C                     | Plug, 2-pin, to EN 175301-803, type C                      |
|                          | 10V24D, 10V24E,<br>10V24F, 10V24P | M12x1 to ISO 20401 in line with EN 61076-2-101             |
| Degree of protection     |                                   | IP65 with plug socket                                      |
| Duty cycle               | [%]                               | 100  |
| Switching time off       | [ms]                              | 65   |
| Switching time on        | [ms]                              | 370  |

| Operating and environmental conditions                   |       |  |
|--|-------|--|
| Operating pressure                                       | [bar] | 3 ... 10   |
| Operating medium   |       | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on the operating/pilot medium                       |       | Lubricated operation possible (in which case lubricated operation will always be required) |
| Ambient temperature                                      | [°C]  | 0 ... +60 (0 ... +50) <sup>1)</sup>  |
| Temperature of medium                                    | [°C]  | 0 ... +60 (0 ... +50) <sup>1)</sup>  |
| Storage temperature                                      | [°C]  | -10 ... +60 (0 ... +50) <sup>1)</sup>  |
| Corrosion resistance class CRC <sup>2)</sup>             |       | 2  |
| CE marking (see declaration of conformity) <sup>3)</sup> |       | To EU Machinery Directive  |
| Food-safe <sup>3)</sup>                                  |       | See supplementary material information (except for solenoid valve)                         |

1) With pressure sensor AD...

2) Corrosion resistance class CRC 2 to Festo standard FN 940070


Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.

3) Additional information: [www.festo.com/catalogue/ms](http://www.festo.com/catalogue/ms) → Support/Downloads.

| Weight [g]                                     |      |
|--|------|
| Soft-start/quick exhaust valve                 | 886  |
| Soft-start/quick exhaust valve with silencer S | 1006 |

| Materials         |                            |
|-------------------|----------------------------|
| Housing           | Die-cast aluminium         |
| Piston rod        | High-alloy stainless steel |
| Seals             | NBR                        |
| Note on materials | RoHS-compliant             |

## Adjusting elements



[1] Screw for adjusting the pressure switchover point

[2] Flow control screw for adjusting the filling time

[3] Manual override at the soft-start/quick exhaust valve:

- detenting, self-resetting as soon as the solenoid coil or manual override on the pilot solenoid valve is actuated (with 10V24, 10V24E, 10V24F, 10V24P)
- none (with 10V24C, 10V24D)

[4] Manual override at the pilot solenoid valve:

- non-detenting, actuation from above (with 10V24/10V24F)
- non-detenting/detenting, actuation from above (with 10V24P)
- none (with 10V24C, 10V24D, 10V24E)

Datasheet MS6-SV-C


Dimensions – Basic version

Download CAD data → [www.festo.com](http://www.festo.com)


With female thread 1/2, with cover plate

Supply voltage  
10V24, 10V24C

Supply voltage  
10V24D, 10V24E, 10V24F,  
10V24P



- 1 = not assigned
- 2 = not assigned
- 3 = com (-)
- 4 = Signal (+) solenoid 14



With silencer S

- [1] Plug connection to EN 175301-803
- [2] Electrical connection M12x1 to ISO 20401 in line with EN 61076-2-101, 4-pin version for connecting cable NEBU-M12
- Flow direction

| Type     | B1 | B4 | B5 | D1   | D2    | D5   | L1  | L2 | L4  |
|----------|----|----|----|------|-------|------|-----|----|-----|
| MS6-SV-C | 62 | 31 | 76 | G1/2 | M12x1 | G3/4 | 144 | 71 | 128 |

| Type     | L8            |                                | L9            |                                |
|----------|---------------|--------------------------------|---------------|--------------------------------|
|          | 10V24, 10V24C | 10V24D, 10V24E, 10V24F, 10V24P | 10V24, 10V24C | 10V24D, 10V24E, 10V24F, 10V24P |
| MS6-SV-C | 33            | 37                             | 24            | 26                             |


† Note: this product conforms to ISO 1179-1 and ISO 228-1.

Dimensions – Pressure gauge/pressure gauge alternatives


Download CAD data → [www.festo.com](http://www.festo.com)

Integrated MS pressure gauge with standard scale AG or red/green scale RG, display unit [bar]

Adapter A4 for EN pressure gauge 1/4, without pressure gauge



→ Flow direction



→ Flow direction

| Type          | B4 | B5   | D4   |
|---------------|----|------|------|
| MS6-SV-...-AG | 31 | 77   | -    |
| MS6-SV-...-RG | 31 | 78.5 | -    |
| MS6-SV-...-A4 | 31 | 78.5 | G1/4 |

† Note: this product conforms to ISO 1179-1 and ISO 228-1.


## Datasheet MS6-SV-C

### Dimensions – Pressure sensor

Download CAD data → [www.festo.com](http://www.festo.com)

Pressure sensor with LCD display AD1 ... AD4

Datasheets → Internet: sde1



[AD1]:  
SDE1-D10-G2-MS...-L-P1-M8 with 1x 3-pin M8 plug, 1 switching output PNP


[AD3]:  
SDE1-D10-G2-MS...-L-PI-M12 with 1x 4-pin M12 plug, 1 switching output PNP and 4 ... 20 mA analogue

[AD2]:  
SDE1-D10-G2-MS...-L-N1-M8 with 1x 3-pin M8 plug, 1 switching output NPN

[AD4]:  
SDE1-D10-G2-MS...-L-NI-M12 with 1x 4-pin M12 plug, 1 switching output NPN and 4 ... 20 mA analogue

Pressure sensor with switching status indicator AD7 ... AD10

Datasheets → Internet: sde5



[AD7]:  
SDE5-D10-O-...-P-M8 with 1x 3-pin M8 plug, threshold value comparator, 1 switching output PNP, N/O contact


[AD9]:  
SDE5-D10-O3-...-P-M8 with 1x 3-pin M8 plug, window comparator, 1 switching output PNP, N/O contact

[AD8]:  
SDE5-D10-C-...-P-M8 with 1x 3-pin M8 plug, threshold value comparator, 1 switching output PNP, N/C contact

[AD10]:  
SDE5-D10-C3-...-P-M8 with 1x 3-pin M8 plug, window comparator, 1 switching output PNP, N/C contact

Pressure sensor with LCD display AD11 ... AD12

Datasheets → Internet: spau



[AD11]:  
SPAU-P10R-MS...-L-PNLK-M12D with 1x 4-pin M12 plug, A-coded, switching output 2x PNP or 2x NPN switchable and 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA analogue

[AD12]:  
SPAU-P10R-MS...-L-PNLK-M8D with 1x 4-pin M8 plug, A-coded, switching output 2x PNP or 2x NPN switchable and 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA analogue

| Type                           | B2 | B3    | B4   | B5 | B6   | D6    | L5   | L6   |
|--------------------------------|----|-------|------|----|------|-------|------|------|
| MS6-SV-...-AD1, AD2            | 31 | 103   | –    | 51 | 32.3 | M8x1  | 35.1 | 46.7 |
| MS6-SV-...-AD3, AD4            |    |       |      |    |      | M12x1 |      | 55.8 |
| MS6-SV-...-AD7, AD8, AD9, AD10 | 31 | 79.1  | –    | 51 | 16   | M8x1  | –    | –    |
| MS6-SV-...-AD11                | 31 | 101.8 | 93.7 | 51 | 32   | M12x1 | 41.2 | 39   |
| MS6-SV-...-AD12                |    |       |      |    |      | M8x1  | 37.9 |      |

† Note: this product conforms to ISO 1179-1 and ISO 228-1.

| Ordering data      |            |               |                      |
|--------------------|------------|---------------|----------------------|
| Size               | Connection | With silencer |                      |
|                    |            | Part no.      | Type                 |
| <b>Cover plate</b> |            |               |                      |
| MS6                | G1/2       | 8001469       | MS6-SV-1/2-C-10V24-S |

## Ordering data – Modular product system MS6N-SV-C

| Ordering table       |   | Conditions | Code           | Enter code |
|----------------------|---|------------|----------------|------------|
| Grid dimension       | [mm] 62   |            |                |            |
| Module no.           | <b>548713</b>   |            |                |            |
| Series               | Standard  |            | <b>MS</b>      | MS         |
| Size                 | 6   |            | <b>6</b>       | 6          |
| Function             | Soft-start/quick exhaust valve  |            | <b>-SV</b>     | -SV        |
| Pneumatic connection | Female thread G1/2  |            | <b>-1/2</b>    |            |
|                      | Connecting plate G1/4   |            | <b>-AGB</b>    |            |
|                      | Connecting plate G3/8   |            | <b>-AGC</b>    |            |
|                      | Connecting plate G1/2   |            | <b>-AGD</b>    |            |
|                      | Connecting plate G3/4   |            | <b>-AGE</b>    |            |
|                      | Connecting plate 1/4 NPT  |            | <b>-AQN</b>    |            |
|                      | Connecting plate 3/8 NPT  |            | <b>-AQP</b>    |            |
|                      | Connecting plate 1/2 NPT  |            | <b>-AQR</b>    |            |
|                      | Connecting plate 3/4 NPT  |            | <b>-AQS</b>    |            |
| Performance Level    | Category 1, single-channel, to EN ISO 13849-1   |            | <b>-C</b>      | -C         |
| Supply voltage       | 24 V DC (plug pattern to EN 175301), 3 ... 10 bar,<br>Manual override<br><ul style="list-style-type: none"> <li>At the soft-start/quick exhaust valve: detenting, self-resetting</li> <li>At the pilot solenoid valve: non-detenting</li> </ul>                               |            | <b>-10V24</b>  |            |
|                      | 24 V DC (plug pattern to EN 175301), 3 ... 10 bar,<br>no manual override  |            | <b>-10V24C</b> |            |
|                      | 24 V DC, M12x1 to ISO 20401 in line with EN 61076-2-101, 3 ... 10 bar, no manual override   |            | <b>-10V24D</b> |            |
|                      | 24 V DC, M12x1 to ISO 20401 in line with EN 61076-2-101, 3 ... 10 bar,<br>Manual override<br><ul style="list-style-type: none"> <li>At the soft-start/quick exhaust valve: detenting, self-resetting</li> <li>At the pilot solenoid valve: none</li> </ul>                    |            | <b>-10V24E</b> |            |
|                      | 24 V DC, M12x1 to ISO 20401 in line with EN 61076-2-101, 3 ... 10 bar,<br>Manual override<br><ul style="list-style-type: none"> <li>At the soft-start/quick exhaust valve: detenting, self-resetting</li> <li>At the pilot solenoid valve: non-detenting</li> </ul>           |            | <b>-10V24F</b> |            |
|                      | 24 V DC, M12x1 to ISO 20401 in line with EN 61076-2-101, 3 ... 10 bar,<br>Manual override<br><ul style="list-style-type: none"> <li>At the soft-start/quick exhaust valve: detenting, self-resetting</li> <li>At the pilot solenoid valve: non-detenting/detenting</li> </ul> |            | <b>-10V24P</b> |            |



## Ordering data – Modular product system MS6N-SV-C

| Ordering table                             |   | Grid dimension | [mm] | 62 | Conditions | Code         | Enter code |
|--|---|----------------|------|----|------------|--------------|------------|
| Silencer                                   | Silencer  |                |      |    |            | <b>-S</b>    |            |
| Pressure gauge/pressure gauge alternatives | MS pressure gauge   | [1]            |      |    |            | <b>-AG</b>   |            |
|  | Adapter for EN pressure gauge 1/4, without pressure gauge   |                |      |    |            | <b>-A4</b>   |            |
|  | Integrated pressure gauge, red/green scale  | [1]            |      |    |            | <b>-RG</b>   |            |
|  | Pressure sensor SDE1 with LCD display, M8 plug, 1 switching output PNP, 3-pin   | [2]            |      |    |            | <b>-AD1</b>  |            |
|  | Pressure sensor SDE1 with LCD display, M8 plug, 1 switching output NPN, 3-pin   | [2]            |      |    |            | <b>-AD2</b>  |            |
|  | Pressure sensor SDE1 with LCD display, M12 plug, 1 switching output PNP, 4-pin, analogue output 4 ... 20 mA                                   | [2]            |      |    |            | <b>-AD3</b>  |            |
|  | Pressure sensor SDE1 with LCD display, M12 plug, 1 switching output NPN, 4-pin, analogue output 4 ... 20 mA                                   | [2]            |      |    |            | <b>-AD4</b>  |            |
|  | Pressure sensor SDE5 with switching status indicator, M8 plug, threshold value comparator, PNP, N/O   | [2]            |      |    |            | <b>-AD7</b>  |            |
|  | Pressure sensor SDE5 with switching status indicator, M8 plug, threshold value comparator, PNP, N/C   | [2]            |      |    |            | <b>-AD8</b>  |            |
|  | Pressure sensor SDE5 with switching status indicator, M8 plug, window comparator, PNP, N/O  | [2]            |      |    |            | <b>-AD9</b>  |            |
|  | Pressure sensor SDE5 with switching status indicator, M8 plug, window comparator, PNP, N/C  | [2]            |      |    |            | <b>-AD10</b> |            |
|  | Pressure sensor SPAU with LCD display, M12 plug 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA                                 | [2]            |      |    |            | <b>-AD11</b> |            |
|  | Pressure sensor SPAU with LCD display, M8 plug 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA                                  | [2]            |      |    |            | <b>-AD12</b> |            |
| Alternative pressure gauge scale           | psi   | [3]            |      |    |            | <b>-PSI</b>  |            |
|  | MPa   | [4]            |      |    |            | <b>-MPA</b>  |            |
| Type of mounting                           | Mounting bracket standard design  |                |      |    |            | <b>-WP</b>   |            |
|  | Mounting bracket for attaching service unit components  | [5]            |      |    |            | <b>-WPM</b>  |            |
|  | Mounting bracket for large wall gap   |                |      |    |            | <b>-WPB</b>  |            |
|  | Mounting bracket centrally at rear (wall mounting top and bottom), connecting plates not required   |                |      |    |            | <b>-WB</b>   |            |
| Tamper protection                          | Complete (manual override at soft-start/quick exhaust valve blocked, setting screws blocked, manual override at pilot solenoid valve blocked) |                |      |    |            | <b>-MK</b>   |            |
| Flow direction                             | Flow direction from right to left   |                |      |    |            | <b>-Z</b>    |            |

[1] **AG, RG** Pressure gauge scale in bar


[2] **AD1 ... AD4, AD7 ... AD12** Measuring range max. 10 bar

[3] **PSI** Only in combination with pressure gauge AG


[4] **MPA** Only in combination with pressure gauge AG or RG

[5] **WPM** Only with connecting plate AGB, AGC, AGD, AGE, AQN, AQP, AQR or AQS


Peripherals overview MS6N-SV-D



Supply voltage  
Code: 10V24



Supply voltage  
Code: 10V24P



**Note**  
Additional accessories:  
• Module connector for combination with size MS4/MS6 or size MS9  
→ Internet: amv rmv  
• Adapter for mounting on profiles  
→ Internet: ipm


## Peripherals overview MS6N-SV-D





| Mounting attachments and accessories |                                |                                       | Single device               |                          | Combination                 |                          | → Page/<br>Internet |
|--------------------------------------|--------------------------------|---------------------------------------|-----------------------------|--------------------------|-----------------------------|--------------------------|---------------------|
|                                      |                                |                                       | Without connecting<br>plate | With connecting<br>plate | Without connecting<br>plate | With connecting<br>plate |                     |
| [1]                                  | MS6-SV-D                       | Soft-start/quick exhaust valve        | ■                           | ■                        | ■                           | ■                        | 19                  |
| [2]                                  | MS6-MV                         | Module connector                      | –                           | ■                        | ■                           | ■                        | ms6-mv              |
| [3]                                  | MS6-WP                         | Mounting bracket                      | ■                           | ■                        | ■                           | ■                        | ms6-wp              |
|                                      | MS6-WPB/WPE/WPM                | Mounting bracket (not shown)          | ■                           | ■                        | ■                           | ■                        | ms6-wp              |
| [4]                                  | MS6-WB                         | Mounting bracket                      | ■                           | ■                        | –                           | –                        | ms6-wb              |
| [5]                                  | MS6-END                        | Cover cap                             | –                           | –                        | ■                           | –                        | ms6-end             |
| [6]                                  | MS6-AEND                       | Mounting plate                        | ■ <sup>1)</sup>             | –                        | ■ <sup>1)</sup>             | –                        | ms6-aend            |
| [7]                                  | MS6-AG...                      | Connecting plate SET                  | –                           | ■ <sup>1)</sup>          | –                           | ■ <sup>1)</sup>          | ms6-ag              |
|                                      | MS6-AQ...                      | Connecting plate SET                  | –                           | ■ <sup>1)</sup>          | –                           | ■ <sup>1)</sup>          | ms6-aq              |
| [8]                                  | 2M8/S3, SMT-8M-A-...-M8D       | Proximity switches                    | ■                           | ■                        | ■                           | ■                        | 19, 19              |
|                                      | 2M12/S3, SMT-8M-A-...-M12      | Proximity switches                    | ■                           | ■                        | ■                           | ■                        | 19, 19              |
|                                      | 2OE/S3, SMT-8M-A-...-OE        | Proximity switches                    | ■                           | ■                        | ■                           | ■                        | 19, 19              |
| [9]                                  | NEBU-M8...-LE3/NEBU-M12...-LE4 | Connecting cable                      | ■                           | ■                        | ■                           | ■                        | 19                  |
| [10]                                 | AD1 ... AD4                    | Pressure sensor SDE1 with LCD display | ■                           | ■                        | ■                           | ■                        | 19                  |
| [11]                                 | A4                             | Adapter for EN pressure gauge 1/4     | ■                           | ■                        | ■                           | ■                        | 19                  |
| [12]                                 | MA                             | Pressure gauge                        | ■                           | ■                        | ■                           | ■                        | 19                  |
| [13]                                 | AG/RG                          | MS pressure gauge                     | ■                           | ■                        | ■                           | ■                        | 19                  |
| [14]                                 | UOS-1-LF                       | Silencer                              | ■                           | ■                        | ■                           | ■                        | 19                  |
| [15]                                 | SO, UOS-1                      | Silencer                              | ■                           | ■                        | ■                           | ■                        | 19                  |
| [16]                                 | MEB-LD                         | Illuminating seal                     | ■                           | ■                        | ■                           | ■                        | 19                  |
| [17]                                 | KMEB                           | Plug socket with cable                | ■                           | ■                        | ■                           | ■                        | 19                  |
| [18]                                 | MSSD-EB                        | Plug socket                           | ■                           | ■                        | ■                           | ■                        | 19                  |
| [19]                                 | NEBU-M12G5                     | Connecting cable                      | ■                           | ■                        | ■                           | ■                        | 19                  |
| [20]                                 | NEBU-M12W5                     | Connecting cable                      | ■                           | ■                        | ■                           | ■                        | 19                  |


1) Module connector MS6-MV [2] or mounting bracket MS6-WP/WPB/WPE/WPM [3] is required for mounting.

## Datasheet MS6-SV-D

### Function



-  - Flow rate  
4300 l/min
-  - Temperature range  
-10 ... +50°C
-  - Operating pressure  
3.5 ... 10 bar
-  - [www.festo.com](http://www.festo.com)



The electropneumatic soft-start/quick exhaust valve is used to reduce pressure quickly and safely and to build up pressure gradually in industrial pneumatic piping systems and terminal equipment.

The MS6-SV-D has two safety functions:

- Safe exhausting
- Protection against unexpected start-up

The MS6-SV-D has a 2-channel design, i.e. it has two internal 2-way valves which can be controlled separately by pilot valves (V1 and V2) on the cover.

The directional control valves are actuated when both coils are energised simultaneously; this moves the MS6-SV-D from the normal position into the switching position. The output pressure p2 rises slowly according to the flow control setting. The main seat opens when the switch-through pressure is reached. The normal position is achieved by switching off both coils. Two proximity switches (S1 and S2) attached to the housing monitor the directional control valves. A further proximity switch (S3) can optionally be added to monitor the soft-start valve.

- Conforms to standard IEC 61508
- Switching time delay can be adjusted using a flow control valve for gradual pressure build-up; main seat opens at approx. 50% of the operating pressure
- Optional pressure sensor

The MS6-SV-D can achieve various categories and safety levels to EN ISO 13849-1 depending on whether the directional control valves are monitored.

When it is integrated appropriately in the control chain and the signals for initial position sensing are correctly linked with the control signals (plausibility checking)

- S1 and S2 Performance  
Level d / Category 3 to  
EN ISO 13849-1 and  
EN ISO 13849-2

- S1, S2 and S3 Performance  
Level e / Category 4 to  
EN ISO 13849-1 and  
EN ISO 13849-2  
are reached.

### Note

To avoid back pressures, it is recommended that the device is operated with the silencer UOS-1. The silencer can be ordered via the modular product system (SO → page 20) or as an accessory (UOS-1 → page 20).

### Note

Only devices that do not impair the pneumatic protective measure of "safe exhausting" may be placed downstream of the MS6-SV-...-D. The MS6-SV-...-D is not approved for use as a press safety valve.

## Datasheet MS6-SV-D

| Safety data  |   |   |
|--|---|---|
| Conforms to  | EN ISO 13849-1 and EN ISO 13849-2   |   |
| Safety function  | Exhausting  |   |
|  | Avoidance of unexpected start-up (pressurisation)                                 |   |
| Performance Level (PL)                                   | With sensing by S1 and S2   | Exhausting: category 3, PL d or category 3, PL e <sup>1)</sup>  |
|  |   | Avoidance of unexpected start-up (pressurisation): category 3, PL d or category 3, PL e <sup>1)</sup> |
|  | With sensing by S1, S2 and S3   | Exhausting: category 4, PL e  |
|  |   | Avoidance of unexpected start-up (pressurisation): category 4, PL e                                   |
| Safety integrity level (SIL)                             | Exhausting: SIL 3   |   |
|  | Avoidance of unexpected start-up (pressurisation): SIL 3                          |   |
| Note on forced checking procedure                        | Switching frequency min. 1/month  |   |
| CE marking (see declaration of conformity) <sup>2)</sup> | To EU Machinery Directive   |   |
| Shock resistance   | Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27 |   |
| Vibration resistance                                     | Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6  |   |

1) Depending on the average number of actuations per year ( $n_{op}$ ).

2) Additional information: [www.festo.com/catalogue/ms](http://www.festo.com/catalogue/ms) → Support/Downloads.

**Note**

The mechanical system is not tested in the controlled (i.e. pressurised) state.

Forced switch on/off: switching frequency should be at least once a month.

If the process-related switching frequency (safe exhausting) is less than once a month,

the machine operator must carry out a forced switch off.


Datasheet MS6-SV-D

| Switching logic  | Voltage at the pilot valve |      | Switching position Proximity switches |    |    | Status  |
|--|----------------------------|------|---------------------------------------|----|----|---|
|  | V1                         | V2   | S1                                    | S2 | S3 |   |
| Pilot valves V1 and V2 are not actuated in the normal position (MS6-SV-D completely exhausted). If both pilot valves are actuated, the MS6-SV-D switches first into switching position 1 and then, when the switch-through pressure is reached, automatically into switching position 2. | 0 V                        | 0 V  | 1                                     | 1  | 1  | <b>Normal position</b><br>Pneumatic connection 1 blocked, passage from pneumatic connection 2 to 3 open   |
|  | 24 V                       | 0 V  | 0                                     | 1  | 1  | <b>Normal position</b><br>Pneumatic connection 1 blocked, passage from pneumatic connection 2 to 3 open   |
|  | 0 V                        | 24 V | 1                                     | 0  | 1  | <b>Normal position</b><br>Reduced flow through flow control valve from pneumatic connection 1 to 2, passage from pneumatic connection 2 to 3 open         |
|  | 24 V                       | 24 V | 0                                     | 0  | 1  | <b>Switching position 1</b><br>Reduced flow through flow control valve from pneumatic connection 1 to 2, passage from pneumatic connection 2 to 3 blocked |
|  | 24 V                       | 24 V | 0                                     | 0  | 0  | <b>Switching position 2</b><br>Full flow from pneumatic connection 1 to 2, passage from pneumatic connection 2 to 3 blocked                               |

| Proximity switch reaction times <sup>1)</sup> |  |  |
|---|--|--|
| Proximity switches                            | Switching on   | Switching off  |
| S1  | Edge change max. 4 s after voltage signal at V1.   | Edge change max. 4 s after voltage drop at V1.   |
| S2  | Edge change max. 4 s after voltage signal at V2.   | Edge change max. 4 s after voltage drop at V2.   |
| S3  | Edge change after voltage signal at V1 and V2.<br>Dependent on operating pressure p1, flow control valve position and system volume p2 | Edge change max. 5 s after voltage drop at V1 and V2.<br>Depending on system volume at p2. |

1) Bounce can occur when the proximity switches undergo an edge change. This bounce can be ignored by taking the reaction times into account. The maximum specified reaction times must be taken into account in the diagnostics. The reaction times are normally shorter.

Sample circuit



- A1, A2: Supply voltage
- S1: Proximity switch S1
- S2: Proximity switch S2
- S3: Proximity switch S3
- NH: Emergency stop (input circuit)
- Safety device: Safety relay unit or safety PLC
- V1: Coil connection, pilot valve V1
- V2: Coil connection, pilot valve V2
- Y1: Diagnostic input 1
- Y2: Diagnostic input 2
- Y3: Diagnostic input 3
- S: Monitored start (start circuit)

## Datasheet MS6-SV-D

| General technical data     |  |
|----------------------------|--|
| Pneumatic connection 1, 2  |  |
| Female thread              | G1/2   |
| Connecting plate AG...     | G1/4, G3/8, G1/2 or G3/4   |
| Connecting plate AQ...     | 1/4 NPT, 3/8 NPT, 1/2 NPT or 3/4 NPT   |
| Pneumatic connection 3     | G1   |
| Actuation type             | Electrical   |
| Design                     | Piston seat  |
| Type of mounting           | Via accessories<br>In-line installation  |
| Mounting position          | Any  |
| Pressure indicator         | Via pressure sensor for indicating the output pressure and electrical output via LCD display<br>Via pressure gauge for displaying the output pressure<br>Via pressure gauge with red/green scale for indicating the output pressure<br>Prepared for G1/4 |
| Position sensing principle | Magnetic piston principle  |
| Valve function             | 3/2-way valve, closed, single solenoid<br>Soft-start function, adjustable  |
| Non-overlapping            | No   |
| Exhaust air function       | Cannot be throttled  |
| Manual override            | None   |
| Reset method               | Mechanical spring  |
| Type of control            | Piloted  |
| Pilot air supply           | Internal   |
| Sealing principle          | Soft   |

† Note: this product conforms to ISO 1179-1 and ISO 228-1.

| Characteristic flow rate values  |                    |
|--|--------------------|
| Pneumatic connection   | Female thread G1/2 |
| <b>Standard nominal flow rate <math>q_{N1}</math> [l/min]</b>                |                    |
| In main flow direction 1 → 2   | 4300               |
| <b>Standard flow rate <math>q_N</math> [l/min], <math>p_2 = 6</math> bar</b> |                    |
| In exhaust direction 2 → 3   | 9000 <sup>2)</sup> |
| <b>C value [l/s*min]</b>   |                    |
| In main flow direction 1 → 2   | 19.3               |
| <b>b value</b>   |                    |
| In main flow direction 1 → 2   | 0.21               |

1) Measured at  $p_1 = 6$  bar and  $p_2 = 5$  bar,  $\Delta p = 1$  bar

2) Measured with reference to atmosphere with silencer UOS-1.

## Datasheet MS6-SV-D

| Electrical data  |           |  |
|--|-----------|--|
| <b>Pilot valve</b>                                       |           |  |
| Characteristic coil data                                 |           | 24 V DC: 1.8 W; permissible voltage fluctuations -15%/+10%                                 |
| Electrical connection                                    | 10V24     | 2x plug, 2-pin, to EN 175301-803, type C   |
|  | 10V24P    | 2x M12x1 to ISO 20401 in line with EN 61076-2-101  |
| Degree of protection                                     |           | IP65 with plug socket  |
| Duty cycle   | [%]       | 100  |
| Max. switching frequency                                 | [Hz]      | 0.5  |
| Switching time off                                       | [ms]      | 40   |
| Switching time on  | [ms]      | 130  |
| <b>Proximity switches</b>                                |           |  |
| Nominal operating voltage                                | [V DC]    | 24   |
| Proximity switch electrical connection                   | 2M8       | 2 x cables with 1x M8 plug, 3-pin, rotatable thread, cable length 0.3 m                    |
|  | 2M12      | 2x cables with 1x M12 plug, 3-pin, rotatable thread, cable length 0.3 m                    |
|  | 2OE       | 2x cable with open end, 3-core, cable length 5 m   |
|  | 2M8 + S3  | 3x cables with 1x M8 plug, 3-pin, rotatable thread, cable length 0.3 m                     |
|  | 2M12 + S3 | 3x cables with 1x M12 plug, 3-pin, rotatable thread, cable length 0.3 m                    |
|  | 2OE + S3  | 3x cable with open end, 3-core, cable length 5 m   |
| Switching element function                               |           | N/O  |
| Measuring principle                                      |           | Magneto-resistive  |
| Signal status indication                                 |           | LED and switching outputs  |
| Switching output   |           | PNP  |
| <b>Operating and environmental conditions</b>            |           |  |
| Operating pressure                                       | [bar]     | 3.5 ... 10   |
| Operating medium   |           | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on the operating/pilot medium                       |           | Lubricated operation possible (in which case lubricated operation will always be required) |
| Ambient temperature                                      | [°C]      | -10 ... +50 (0 ... +50) <sup>1)</sup>  |
| Temperature of medium                                    | [°C]      | -10 ... +50 (0 ... +50) <sup>1)</sup>  |
| Storage temperature                                      | [°C]      | -10 ... +50 (0 ... +50) <sup>1)</sup>  |
| Corrosion resistance class CRC <sup>2)</sup>             |           | 2  |
| Noise level  | [dB(A)]   | 75 (with silencer UOS-1)   |
| CE marking (see declaration of conformity) <sup>3)</sup> |           | To EU Machinery Directive  |
| UL certification <sup>3)</sup>                           |           | c UL us - Recognized (OL)  |
| Certification  |           | RCM  |
| KC marking   |           | KC EMC   |

1) With pressure sensor AD...

2) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.

3) Additional information: [www.festo.com/catalogue/ms](http://www.festo.com/catalogue/ms) → Support/Downloads.




## Datasheet MS6-SV-D

| Weight [g]   |      |
|--|------|
| Soft-start/quick exhaust valve                     | 1900 |
| Soft-start/quick exhaust valve with silencer UOS-1 | 2110 |

| Materials         |                            |
|-------------------|----------------------------|
| Housing           | Die-cast aluminium         |
| Piston rod        | High-alloy stainless steel |
| Seals             | NBR                        |
| Note on materials | RoHS-compliant             |

## Switching pressure

Pressure  $p$  as a function of time  $t$ 

- [1] Tolerance range
- [2] Switching point
- [3] Filling time is adjustable via a flow control valve

**Note**  
 The +20%/–10% switching pressure tolerance refers to the operating pressure  $p_1$ .  
 Example: a switching pressure from 1.6 bar to 2.8 bar is permissible at an operating pressure of 4 bar.


Datasheet MS6-SV-D

Dimensions – Basic version

Download CAD data → [www.festo.com](http://www.festo.com)

With supply voltage 10V24, with female thread 1/2, with cover plate

With supply voltage 10V24P, with female thread 1/2, with cover plate



- [1] Adjusting screw for throttle valve
- [2] Silencer UOS-1
- [3] Extended sensing,
  - Variant S3: additional third proximity switch SMT, connection depends on the selected connection technology

- [4] Connection technology,
  - Variant 2M8: 2 proximity switches SMT with cable (1x M8 plug, 3-pin, rotatable thread, cable length 0.3 m)
  - Variant 2M12: 2 proximity switches SMT with cable (1x M12 plug, 3-pin, rotatable thread, cable length 0.3 m)
  - Variant 2OE: 2 proximity switches SMT with cable (open end, 3-core, cable length 5 m)

- [5] Supply voltage,
  - Variant 10V24: electrical connection to EN 175301-803, 2x plugs, 2-pin, type C
  - Variant 10V24P: electrical connection 2x M12x1 to ISO 20401 in line with EN 61076-2-101, 4-pin version for connecting cable NEBU-M12

→ Flow direction

| Type                | B1 | B2 | B3 | B4 | B5 | D1   | D5 | D6<br>Ø | L1  | L2  | L4  | L7  | L9 |
|---------------------|----|----|----|----|----|------|----|---------|-----|-----|-----|-----|----|
| MS6-SV-1/2-D-10V24  | 62 | 45 | 90 | 31 | 76 | G1/2 | G1 | 55      | 257 | 110 | 147 | 147 | 9  |
| MS6-SV-1/2-D-10V24P |    |    |    |    |    |      |    |         | 262 | 115 |     |     | 11 |

† Note: this product conforms to ISO 1179-1 and ISO 228-1.


## Datasheet MS6-SV-D

### Dimensions – Pressure gauge/pressure gauge alternatives

Download CAD data → [www.festo.com](http://www.festo.com)

Integrated MS pressure gauge with standard scale AG or red/green scale RG, display unit [bar]

Adapter A4 for EN pressure gauge 1/4, without pressure gauge



| Type                | B2 | B3   | B4 | B5   | D4   |
|---------------------|----|------|----|------|------|
| MS6-SV-...-D-...-AG | 44 | 90   | 31 | 77   | –    |
| MS6-SV-...-D-...-RG | 44 | 91.5 | 31 | 78.5 | –    |
| MS6-SV-...-D-...-A4 | 44 | 91.5 | 31 | 78.5 | G1/4 |


† Note: this product conforms to ISO 1179-1 and ISO 228-1.

### Dimensions – Pressure sensor

Download CAD data → [www.festo.com](http://www.festo.com)

Pressure sensor with LCD display AD1 ... AD4

Datasheets → Internet: sde1



[AD1]:  
SDE1-D10-G2-MS...-L-P1-M8 with 1x 3-pin M8 plug, 1 switching output PNP

[AD3]:  
SDE1-D10-G2-MS...-L-PI-M12 with 1x 4-pin M12 plug, 1 switching output PNP and 4 ... 20 mA analogue

[AD2]:  
SDE1-D10-G2-MS...-L-N1-M8 with 1x 3-pin M8 plug, 1 switching output NPN

[AD4]:  
SDE1-D10-G2-MS...-L-NI-M12 with 1x 4-pin M12 plug, 1 switching output NPN and 4 ... 20 mA analogue

| Type                | B2 | B3  | B4 | B5 | B6   | D6    | L5   | L6   |
|---------------------|----|-----|----|----|------|-------|------|------|
| MS6-SV-...-AD1, AD2 | 31 | 103 | –  | 51 | 32.3 | M8x1  | 35.1 | 46.7 |
| MS6-SV-...-AD3, AD4 |    |     |    |    |      | M12x1 |      | 55.8 |

† Note: this product conforms to ISO 1179-1 and ISO 228-1.

## Datasheet MS6-SV-D

| Ordering data  |            |   |   |                                |
|--|------------|---|---|--------------------------------|
| Size   | Connection | Description   | With silencer and MS pressure gauge with standard scale, display unit [bar] |                                |
|  |            |   | Part no.  | Type                           |
| <b>Electrical connection to EN 175301-803 (2x plugs, 2-pin, type C), 2 proximity switches SMT with cable (1x M8 plug, 3-pin, rotatable thread, cable length 0.3 m)</b>               |            |   |   |                                |
| MS6  | G1/2       | Without silencer, with cover plate  | 8038489   | MS6-SV-1/2-D-10V24-2M8         |
| MS6  | G1/2       | With silencer and MS pressure gauge with standard scale, display unit [bar] | 8038490   | MS6-SV-1/2-D-10V24-2M8-SO-AG   |
| <b>Electrical connection to IEC 61076-2-101 (2x M12x1 plugs, 2-pin for NEBU-M12), 2 proximity switches SMT with cable (1x M12 plug, 3-pin, rotatable thread, cable length 0.3 m)</b> |            |   |   |                                |
| MS6  | G1/2       | With silencer and MS pressure gauge with standard scale, display unit [bar] | 8038491   | MS6-SV-1/2-D-10V24P-2M12-SO-AG |
| <b>Electrical connection to EN 175301-803 (2x plugs, 2-pin, type C), 2 proximity switches SMT with cable (open end, 3-core, cable length 5 m)</b>                                    |            |   |   |                                |
| MS6  | G1/2       | With silencer and MS pressure gauge with standard scale, display unit [bar] | 8038492   | MS6-SV-1/2-D-10V24-20E-SO-AG   |

## Ordering data – Modular product system MS6N-SV-D

| Ordering table                             |  | Conditions | Code           | Enter code |
|--|--|------------|----------------|------------|
| Grid dimension                             | [mm] 62  |            |                |            |
| Module no.                                 | <b>548713</b>  |            |                |            |
| Series                                     | Standard   |            | <b>MS</b>      | MS         |
| Size                                       | 6  |            | <b>6</b>       | 6          |
| Function                                   | Soft-start/quick exhaust valve   |            | <b>-SV</b>     | -SV        |
| Pneumatic connection                       | Female thread G1/2   |            | <b>-1/2</b>    |            |
|  | Connecting plate G1/4  |            | <b>-AGB</b>    |            |
|  | Connecting plate G3/8  |            | <b>-AGC</b>    |            |
|  | Connecting plate G1/2  |            | <b>-AGD</b>    |            |
|  | Connecting plate G3/4  |            | <b>-AGE</b>    |            |
|  | Connecting plate 1/4 NPT   |            | <b>-AQN</b>    |            |
|  | Connecting plate 3/8 NPT   |            | <b>-AQP</b>    |            |
|  | Connecting plate 1/2 NPT   |            | <b>-AQR</b>    |            |
|  | Connecting plate 3/4 NPT   |            | <b>-AQS</b>    |            |
| Performance Level                          | Category 3, 2-channel to EN ISO 13849-1  |            | <b>-D</b>      | -D         |
| Supply voltage                             | 24 V DC (plug pattern to EN 175301)  |            | <b>-10V24</b>  |            |
|  | 24 V DC, M12x1 to ISO 20401 in line with EN 61076-2-101  |            | <b>-10V24P</b> |            |
| Connection technology                      | 2 proximity switches SMT with cable (1x M8 plug, 3-pin, rotatable thread, cable length 0.3 m)                                      |            | <b>-2M8</b>    |            |
|  | 2 proximity switches SMT with cable (1x M12 plug, 3-pin, rotatable thread, cable length 0.3 m)                                     |            | <b>-2M12</b>   |            |
|  | 2 proximity switches SMT with cable (open end, 3-core, cable length 5 m)   |            | <b>-2OE</b>    |            |
| Extended sensing                           | Additional proximity switch SMT; required to achieve Performance Level e; connection depends on the selected connection technology |            | <b>-S3</b>     |            |
| Silencer                                   | Open silencer  |            | <b>-S0</b>     |            |
| Pressure gauge/pressure gauge alternatives | MS pressure gauge  | [1]        | <b>-AG</b>     |            |
|  | Adapter for EN pressure gauge 1/4, without pressure gauge  |            | <b>-A4</b>     |            |
|  | Integrated pressure gauge, red/green scale   | [1]        | <b>-RG</b>     |            |
|  | Pressure sensor SDE1 with LCD display, M8 plug, 1 switching output PNP, 3-pin  | [2]        | <b>-AD1</b>    |            |
|  | Pressure sensor SDE1 with LCD display, M8 plug, 1 switching output NPN, 3-pin  | [2]        | <b>-AD2</b>    |            |
|  | Pressure sensor SDE1 with LCD display, M12 plug, 1 switching output PNP, 4-pin, analogue output 4 ... 20 mA                        | [2]        | <b>-AD3</b>    |            |
|  | Pressure sensor SDE1 with LCD display, plug M12, 1 switching output NPN, 4-pin, analogue output 4 ... 20 mA                        | [2]        | <b>-AD4</b>    |            |
| Alternative pressure gauge scale           | psi  | [3]        | <b>-PSI</b>    |            |
|  | MPa  | [4]        | <b>-MPA</b>    |            |
| Type of mounting                           | Mounting bracket standard design   |            | <b>-WP</b>     |            |
|  | Mounting bracket for attaching service unit components   | [5]        | <b>-WPM</b>    |            |
|  | Mounting bracket for large wall gap  |            | <b>-WPB</b>    |            |
|  | Mounting bracket centrally at rear (wall mounting top and bottom), connecting plates not required                                  |            | <b>-WB</b>     |            |
| UL certification                           | cULus, ordinary location for Canada and USA  |            | <b>-UL1</b>    |            |
| Flow direction                             | Flow direction from right to left  |            | <b>-Z</b>      |            |

[1] **AG, RG** Pressure gauge scale in bar


[2] **AD1 ... AD4** Measuring range max. 10 bar


[3] **PSI** Only in combination with pressure gauge AG

[4] **MPA** Only in combination with pressure gauge AG or RG

[5] **WPM** Only with connecting plate AGB, AGC, AGD, AGE, AQN, AQP, AQR or AQS

Peripherals overview MS6N-SV-E



 **Note**  
 Additional accessories:  
 • Module connector for combination with size MS4/MS6 or size MS9  
 → Internet: amv rmv  
 • Adapter for mounting on profiles  
 → Internet: ipm


## Peripherals overview MS6N-SV-E

| Mounting attachments and accessories |                                |                                       | Single device            |                       | Combination              |                       | → Page/<br>Internet |
|--------------------------------------|--------------------------------|---------------------------------------|--------------------------|-----------------------|--------------------------|-----------------------|---------------------|
|                                      |                                |                                       | Without connecting plate | With connecting plate | Without connecting plate | With connecting plate |                     |
| [1]                                  | MS6-SV-E                       | Soft-start/quick exhaust valve        | ■                        | ■                     | ■                        | ■                     | 31                  |
| [2]                                  | MS6-MV                         | Module connector                      | –                        | –                     | ■                        | ■                     | ms6-mv              |
| [3]                                  | MS6-WPB                        | Mounting bracket                      | ■                        | ■                     | ■                        | ■                     | ms6-wpb             |
| [4]                                  | MS6-WPE                        | Mounting bracket                      | ■                        | ■                     | ■                        | ■                     | ms6-wpe             |
| [5]                                  | MS6-END                        | Cover cap                             | –                        | –                     | ■                        | –                     | ms6-end             |
| [6]                                  | MS6-AEND                       | Mounting plate                        | ■ <sup>1)</sup>          | –                     | ■ <sup>1)</sup>          | –                     | ms6-aend            |
| [7]                                  | MS6-AG...                      | Connecting plate SET                  | –                        | ■ <sup>1)</sup>       | –                        | ■ <sup>1)</sup>       | ms6-ag              |
|                                      | MS6-AQ...                      | Connecting plate SET                  | –                        | ■ <sup>1)</sup>       | –                        | ■ <sup>1)</sup>       | ms6-aq              |
| [8]                                  | NEBU-M8...-LE3/NEBU-M12...-LE4 | Connecting cable                      | ■                        | ■                     | ■                        | ■                     | 31                  |
| [9]                                  | AD1 ... AD4                    | Pressure sensor SDE1 with LCD display | ■                        | ■                     | ■                        | ■                     | 31                  |
| [10]                                 | A4                             | Adapter for EN pressure gauge 1/4     | ■                        | ■                     | ■                        | ■                     | 31                  |
| [11]                                 | MA                             | Pressure gauge                        | ■                        | ■                     | ■                        | ■                     | 31                  |
| [12]                                 | AG/RG                          | MS pressure gauge                     | ■                        | ■                     | ■                        | ■                     | 31                  |
| [13]                                 | UOS-1-LF                       | Silencer                              | ■                        | ■                     | ■                        | ■                     | 31                  |
| [14]                                 | UOS-1                          | Silencer                              | ■                        | ■                     | ■                        | ■                     | 31                  |
| [15]                                 | NECA                           | Multi-pin plug socket                 | ■                        | ■                     | ■                        | ■                     | 31                  |

1) Module connector MS6-MV [2] or mounting bracket MS6-WPB [3] or MS6-WPE [4] is required for assembly.

## Datasheet MS6-SV-E

### Function



- Flow rate  
4300 l/min
- Temperature range  
-10 ... +50°C
- Operating pressure  
3.5 ... 10 bar
- [www.festo.com](http://www.festo.com)



The electropneumatic soft-start/quick exhaust valve is used to reduce pressure quickly and safely and to build up pressure gradually in industrial pneumatic piping systems and terminal equipment.

The device is a self-testing, redundant mechatronic system conforming to the requirements of EN ISO 13849-1. The

safety-related pneumatic protection objective of safe exhausting is also guaranteed in the event of faults inside the valve (e.g. due to wear, contamination, electronic faults). The 2-channel design and its monitoring enables the device to meet controller category 3 and 4 requirements. This

enables a Performance Level of max. "e".

The device receives the secure enable signals (EN1/EN2) via the electrical connection (multi-pin plug socket NECA Sub-D, 9-pin or AS-i connecting cable). The signals are generated by commercially available electronic or electromechanical safety switching de-

vices which monitor the protective equipment of the machine (e.g. emergency stop, light curtain, electrical door switch of a protective enclosure, etc.).

- Performance Level "e" / Category 4 to EN ISO 13849-1
- Conforms to standard IEC 61508
- Switching time delay adjustable via a flow control valve for gradual pressure build-up
- Optional pressure sensor

- **Note**  
The MS6N-SV...-E-10V24 should only be used in combination with the multi-pin plug socket NECA for which it is approved.  
The multi-pin plug socket can be ordered via the modular product system (MP → page 32) or as an accessory (NECA → page 32).

- **Note**  
To avoid back pressures, it is recommended that the device is operated with the silencer UOS-1. The silencer can be ordered via the modular product system (SO → page 32) or as an accessory (UOS-1 → page 32).

- **Note**  
Only devices that do not impair the pneumatic protective measure "safe exhausting" may be placed downstream of the MS6-SV...-E. The MS6-SV...-E is not approved for use as a press safety valve.

| Safety data  |  |
|--|--|
| Type   | MS6-SV...-E-10V24  |
| Conforms to  | EN ISO 13849-1   |
| Safety function  | Exhausting<br>Avoidance of unexpected start-up (pressurisation)  |
| Performance Level (PL)                                   | Exhausting: up to category 4, PL e<br>Prevention of unexpected start-up (pressurisation): up to category 4, PL e |
| Safety integrity level (SIL)                             | Exhausting: SIL 3<br>Avoidance of unexpected start-up (pressurisation): SIL 3                                    |
| Note on forced checking procedure                        | Switching frequency min. 1/month   |
| Certificate issuing authority <sup>1)</sup>              | IFA 1001180  |
| CE marking (see declaration of conformity) <sup>1)</sup> | To EU Machinery Directive<br>To EU EMC Directive   |
| Shock resistance   | Shock test with severity level 2 in accordance with FN 942017-5 and EN 60068-2-27                                |
| Vibration resistance                                     | Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6                                 |

<sup>1)</sup> Additional information: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/...) → Support/Downloads.

- **Note**  
The mechanical system is not tested in the controlled (i.e. pressurised) state.

Forced switch on/off: switching frequency should be at least once a month.

If the process-related switching frequency (safe exhausting) is less than once a month,

the machine operator must carry out a forced switch off.





Datasheet MS6-SV-E

Operational principle of the multi-pin plug socket NECA


| Enable signal status |      | Status of MS6-SV...-E-10V24 with multi-pin plug socket |   |  |
|----------------------|------|--|---|--|
| EN1                  | EN2  | NECA-...-MP1   | NECA-...-MP3                              | NECA-...-MP5   |
| 0 V                  | 0 V  | Unpressurised  | MS6-SV...-E-10V24 switches to fault mode. | MS6N-SV...-E-10V24 does not switch to fault mode, but remains in the safe, unpressurised state.<br><b>Note:</b><br>Detection of cross-circuits and error detection/evaluation necessary via external controller. |
| 0 V                  | 24 V | MS6-SV...-E-10V24 switches to fault mode.              | Pressurised                               | Pressurised  |
| 24 V                 | 24 V | Pressurised  | MS6-SV...-E-10V24 switches to fault mode. | MS6N-SV...-E-10V24 does not switch to fault mode, but remains in the safe, unpressurised state.<br><b>Note:</b><br>Detection of cross-circuits and error detection/evaluation necessary via external controller. |
| 24 V                 | 0 V  | MS6-SV...-E-10V24 switches to fault mode.              | Unpressurised                             | Unpressurised  |

MS6-SV...-E-10V24 with multi-pin plug socket NECA

NECA-...-MP1



- Static enable signals (EN1 = 24 V, EN2 = 24 V).




- Clocked enable signals (EN1 = 0 ... 24 V, EN2 = 0 ... 24 V) for detection of cross-circuits.  
Detection of cross-circuits by clock pulse signals is always carried out by the safety relay unit/safety PLC.

**Note**  
Since the clock pulse outputs from different controller manufacturers are not standardised, their usability must be checked in each case. If the clock pulse is outside the specified limits, the MS6N-SV...-E-10V24 detects it as an error and a safe shut-down is initiated.


Datasheet MS6-SV-E

MS6-SV-...-E-10V24 with multi-pin plug socket NECA

NECA-...-MP3




**Note**  
The multi-pin plug socket NECA-S1G9-P9-MP3 is intended for conventional circuitry with electro-mechanical safety relays. If problems arise when used with bipolar semiconductor outputs, use the multi-pin plug socket NECA-S1G9-P9-MP5.




- Static enable signals with opposite potentials.
- Time delay of the level change of the enable signals is monitored.
- Behaviour on detection of a cross-circuit:
  - MS6N-SV-...-E-10V24 in exhausted state: remains in safe state and goes into error mode.
  - MS6N-SV-...-E-10V24 in pressurised state: goes into safe state and goes into error mode.

NECA-...-MP5



**Note**  
A cross-circuit between the enable signals EN1/EN2 is not detected and does not cause an error response. The system is pressurised only if the enable signals are applied correctly.



- Static enable signals with opposite potentials.
- Time delay of the level change of the enable signals is not monitored.
- Behaviour on detection of a cross-circuit (by upstream safety relay unit/PLC):
  - MS6N-SV-...-E-10V24 in exhausted state: remains in safe state and does not go into error mode.
  - MS6N-SV-...-E-10V24 in pressurised state: goes into safe state and does not go into error mode.
- Enable signals are galvanically separated from the supply voltage.

**Note**  
The time delay between EN1 and EN2 must be automatically determined. The duration of the delay is not evaluated.

## Datasheet MS6-SV-E

| General technical data     |  |
|----------------------------|--|
| Pneumatic connection 1, 2  |  |
| Female thread              | G1/2   |
| Connecting plate AG...     | G1/4, G3/8, G1/2 or G3/4   |
| Connecting plate AQ...     | 1/4 NPT, 3/8 NPT, 1/2 NPT or 3/4 NPT   |
| Pneumatic connection 3     | G1   |
| Actuation type             | Electrical   |
| Design                     | Piston seat  |
| Type of mounting           | Via accessories<br>In-line installation  |
| Mounting position          | Any  |
| Pressure indicator         | Via pressure sensor for indicating the output pressure and electrical output via LCD display<br>Via pressure gauge for displaying the output pressure<br>Via pressure gauge with red/green scale for indicating the output pressure<br>Prepared for G1/4 |
| Position sensing principle | Magnetic piston principle  |
| Valve function             | 3/2-way valve, closed, single solenoid<br>Soft-start function, adjustable  |
| Non-overlapping            | No   |
| Exhaust air function       | Cannot be throttled  |
| Manual override            | None   |
| Reset method               | Mechanical spring  |
| Type of control            | Piloted  |
| Pilot air supply           | Internal   |
| Sealing principle          | Soft   |

† Note: This product conforms to ISO 1179-1 and ISO 228-1.

| Characteristic flow rate values  |                    |
|--|--------------------|
| Pneumatic connection   | Female thread G1/2 |
| <b>Standard nominal flow rate <math>q_{N^{(1)}}</math> [l/min]</b>           |                    |
| In main flow direction 1 → 2   | 4300               |
| <b>Standard flow rate <math>q_N</math> [l/min], <math>p_2 = 6</math> bar</b> |                    |
| In exhaust direction 2 → 3   | 9000 <sup>2)</sup> |
| <b>C value [l/s*min]</b>   |                    |
| In main flow direction 1 → 2   | 19.3               |
| <b>b value</b>   |                    |
| In main flow direction 1 → 2   | 0.21               |

1) Measured at  $p_1 = 6$  bar and  $p_2 = 5$  bar,  $\Delta p = 1$  bar

2) Measured with reference to atmosphere with silencer UOS-1.

| Electrical data                                  |                          |
|--|--------------------------|
| Type   | MS6-SV-...-E-10V24       |
| Electrical connection                            | Sub-D 9-polig            |
| Nominal operating voltage [V DC]                 | 24                       |
| Permissible voltage fluctuations [%]             | ±10                      |
| Operating voltage range for AS-In-terface [V DC] | –                        |
| Duty cycle [%]                                   | 100                      |
| Max. switching frequency [Hz]                    | 0.5                      |
| Switching time off [ms]                          | 40                       |
| Switching time on [ms]                           | 130                      |
| Signal status indication                         | LED and floating contact |
| Degree of protection                             | IP65 with plug socket    |

## Datasheet MS6-SV-E

| Operating and environmental conditions                   |  |
|--|--|
| Type   | MS6-SV-...-E-10V24   |
| Operating pressure [bar]                                 | 3.5 ... 10   |
| Operating medium   | Compressed air to ISO 8573-1:2010 [7:4:4]  |
| Note on the operating/pilot medium                       | Lubricated operation possible (in which case lubricated operation will always be required) |
| Ambient temperature [°C]                                 | -10 ... +50 (0 ... +50) <sup>1)</sup>  |
| Temperature of medium [°C]                               | -10 ... +50 (0 ... +50) <sup>1)</sup>  |
| Storage temperature [°C]                                 | -10 ... +50 (0 ... +50) <sup>1)</sup>  |
| Corrosion resistance class CRC <sup>2)</sup>             | 2  |
| Noise level [dB(A)]                                      | 75 (with silencer UOS-1)   |
| CE marking (see declaration of conformity) <sup>3)</sup> | To EU EMC Directive  |
|  | To EU Machinery Directive  |
| UL certification <sup>3)</sup>                           | cUL us - Recognized (OL)   |
| Certification  | RCM  |
| KC marking   | KC EMC   |

1) With pressure sensor AD...

2) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.

3) Additional information: [www.festo.com/catalogue/ms](http://www.festo.com/catalogue/ms) → Support/Downloads.


| Weight [g]   |      |
|--|------|
| Soft-start/quick exhaust valve                     | 2000 |
| Soft-start/quick exhaust valve with silencer UOS-1 | 2200 |

| Materials         |                            |
|-------------------|----------------------------|
| Housing           | Die-cast aluminium         |
| Piston rod        | High-alloy stainless steel |
| Seals             | NBR                        |
| Note on materials | RoHS-compliant             |

## Datasheet MS6-SV-E

### Switching point

Pressure  $p$  as a function of time  $t$




- [1] Tolerance range
- [2] Switching point
- [3] Regulating screw for flow control valve

**Note**  
The +20%/–10% switching point tolerance refers to the operating pressure  $p_1$ .  
Example: A switching point from 1.6 bar to 2.8 bar is permissible at an operating pressure of 4 bar.

### Dimensions – Basic version

Download CAD data → [www.festo.com](http://www.festo.com)



- [1] Regulating screw for flow control valve
- [2] Silencer UOS-1
- [3] Multi-pin plug socket NECA
- [4] Dimension without cable

| Type               | B1 | B2 | B3  | B4 | D1   | D5 | D6 | L1  | L2 | L3 | L4  |
|--------------------|----|----|-----|----|------|----|----|-----|----|----|-----|
| MS6-SV-1/2-E-10V24 | 62 | 59 | 104 | 23 | G1/2 | G1 | 55 | 228 | 81 | 61 | 145 |

Note: This product conforms to ISO 1179-1 and ISO 228-1.



Datasheet MS6-SV-E

Dimensions – Pressure gauge/pressure gauge alternatives

Download CAD data → [www.festo.com](http://www.festo.com)

Integrated MS pressure gauge AG with standard scale AG or red/green scale RG, display unit [bar]

Adapter A4 for EN pressure gauge 1/4, without pressure gauge



| Type                | B2 | B3    | D4   |
|---------------------|----|-------|------|
| MS6-SV-...-E-...-AG | 59 | 105   | -    |
| MS6-SV-...-E-...-RG | 59 | 106.5 | -    |
| MS6-SV-...-E-...-A4 | 59 | 106.5 | G1/4 |


Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions – Pressure sensor

Download CAD data → [www.festo.com](http://www.festo.com)

Pressure sensor with LCD display AD1 ... AD4

Datasheets → Internet: sde1



[AD1]:  
SDE1-D10-G2-MS...-L-P1-M8 with 1x 3-pin M8 plug, 1 switching output PNP

[AD3]:  
SDE1-D10-G2-MS...-L-PI-M12 with 1x 4-pin M12 plug, 1 switching output PNP and 4 ... 20 mA analogue

[AD2]:  
SDE1-D10-G2-MS...-L-N1-M8 with 1x 3-pin M8 plug, 1 switching output NPN

[AD4]:  
SDE1-D10-G2-MS...-L-NI-M12 with 1x 4-pin M12 plug, 1 switching output NPN and 4 ... 20 mA analogue

| Type                | B2 | B3  | B4 | B5 | B6   | D6    | L5   | L6   |
|---------------------|----|-----|----|----|------|-------|------|------|
| MS6-SV-...-AD1, AD2 | 31 | 103 | -  | 51 | 32.3 | M8x1  | 35.1 | 46.7 |
| MS6-SV-...-AD3, AD4 |    |     |    |    |      | M12x1 |      | 55.8 |

Note: This product conforms to ISO 1179-1 and ISO 228-1.

Ordering data – Supply voltage 10V24

| Size   | Connection | Without silencer |                        | With silencer |                          |
|--|------------|------------------|------------------------|---------------|--------------------------|
|  |            | Part no.         | Type                   | Part no.      | Type                     |
| <b>MS pressure gauge, display unit [bar]</b>                 |            |                  |                        |               |                          |
| MS6  | G1/2       | 548715           | MS6-SV-1/2-E-10V24-AG  | 548717        | MS6-SV-1/2-E-10V24-SO-AG |
| <b>Pressure sensor with LCD display, M8 plug, PNP, 3-pin</b> |            |                  |                        |               |                          |
| MS6  | G1/2       | 562580           | MS6-SV-1/2-E-10V24-AD1 | -             | -                        |

## Ordering data – Modular product system MS6N-SV-E

| Ordering table                             |   | Grid dimension [mm] | 62            | Conditions | Code          | Enter code |
|--|---|---------------------|---------------|------------|---------------|------------|
| Module no.                                 |   |                     | <b>548713</b> |            |               |            |
| Series                                     | Standard  |                     |               |            | <b>MS</b>     | MS         |
| Size                                       | 6   |                     |               |            | <b>6</b>      | 6          |
| Function                                   | Soft-start/quick exhaust valve  |                     |               |            | <b>-SV</b>    | -SV        |
| Pneumatic connection                       | Female thread G1/2  |                     |               |            | <b>-1/2</b>   |            |
|  | Connecting plate G1/4   |                     |               |            | <b>-AGB</b>   |            |
|  | Connecting plate G3/8   |                     |               |            | <b>-AGC</b>   |            |
|  | Connecting plate G1/2   |                     |               |            | <b>-AGD</b>   |            |
|  | Connecting plate G3/4   |                     |               |            | <b>-AGE</b>   |            |
|  | Connecting plate 1/4 NPT  |                     |               |            | <b>-AQN</b>   |            |
|  | Connecting plate 3/8 NPT  |                     |               |            | <b>-AQP</b>   |            |
|  | Connecting plate 1/2 NPT  |                     |               |            | <b>-AQR</b>   |            |
|  | Connecting plate 3/4 NPT  |                     |               |            | <b>-AQS</b>   |            |
| Performance Level                          | Category 4, 2-channel with self-monitoring to ISO 13849-1   |                     |               |            | <b>-E</b>     | -E         |
| Supply voltage                             | 24 V DC   |                     |               |            | <b>-10V24</b> |            |
| Silencer                                   | Open silencer   |                     |               |            | <b>-SO</b>    |            |
| Pressure gauge/pressure gauge alternatives | MS pressure gauge   |                     | [1]           |            | <b>-AG</b>    |            |
|  | Adapter for EN pressure gauge 1/4, without pressure gauge   |                     |               |            | <b>-A4</b>    |            |
|  | Integrated pressure gauge, red/green scale  |                     | [1]           |            | <b>-RG</b>    |            |
|  | Pressure sensor SDE1 with LCD display, M8 plug, 1 switching output PNP, 3-pin   |                     | [2]           |            | <b>-AD1</b>   |            |
|  | Pressure sensor SDE1 with LCD display, M8 plug, 1 switching output NPN, 3-pin   |                     | [2]           |            | <b>-AD2</b>   |            |
|  | Pressure sensor SDE1 with LCD display, M12 plug, 1 switching output PNP, 4-pin, analogue output 4 ... 20 mA   |                     | [2]           |            | <b>-AD3</b>   |            |
|  | Pressure sensor SDE1 with LCD display, M12 plug, 1 switching output NPN, 4-pin, analogue output 4 ... 20 mA   |                     | [2]           |            | <b>-AD4</b>   |            |
| Alternative pressure gauge scale           | psi   |                     | [3]           |            | <b>-PSI</b>   |            |
|  | MPa   |                     | [4]           |            | <b>-MPA</b>   |            |
| Multi-pin plug socket                      | Sub-D, 9-pin, screw terminal, without cable, static enable signals (EN1 = 24 V, EN2 = 24 V)   |                     |               |            | <b>-MP1</b>   |            |
|  | Sub-D, 9-pin, screw terminal, without cable, static enable signals (EN1 = 0 V, EN2 = 24 V), Cross-circuit detection possible                            |                     |               |            | <b>-MP3</b>   |            |
|  | Sub-D, 9-pin, screw terminal, without cable, static enable signals (EN1 = 0 V, EN2 = 24 V), galvanic isolation of enable signal from the supply voltage |                     |               |            | <b>-MP5</b>   |            |
| Type of mounting                           | Mounting bracket for large mounting spacing   |                     |               |            | <b>-WPB</b>   |            |
| UL certification                           | cULus, ordinary location for Canada and USA   |                     |               |            | <b>-UL1</b>   |            |
| Flow direction                             | Flow direction from right to left   |                     |               |            | <b>-Z</b>     |            |

[1] **AG, RG** Pressure gauge scale in bar

[2] **AD1 ... AD4** Measuring range max. 10 bar

[3] **PSI** Only in combination with pressure gauge AG

[4] **MPA** Only in combination with pressure gauge AG or RG

## Type codes MS9-SV

|            |               |
|------------|---------------|
| <b>001</b> | <b>Series</b> |
| <b>MS</b>  | MS series     |

|            |                      |
|------------|----------------------|
| <b>002</b> | <b>Size</b>          |
| <b>9</b>   | Grid dimension 90 mm |

|            |                                |
|------------|--------------------------------|
| <b>003</b> | <b>Function</b>                |
| <b>SV</b>  | Soft-start/quick exhaust valve |

|             |   |
|-------------|---|
| <b>004</b>  | <b>Pneumatic connection</b>                               |
| <b>3/4</b>  | Female thread G3/4  |
| <b>1</b>    | Female thread G1  |
| <b>AGD</b>  | Sub-base G1/2   |
| <b>AGE</b>  | Sub-base G3/4   |
| <b>AGF</b>  | Sub-base G1   |
| <b>AGG</b>  | Connecting plate G1 1/4                                   |
| <b>AGH</b>  | Connecting plate G1 1/2                                   |
| <b>N3/4</b> | Female thread 3/4 NPT                                     |
| <b>N1</b>   | Female thread 1 NPT                                       |
| <b>AQR</b>  | Sub-base 1/2 NPT  |
| <b>AQS</b>  | Sub-base 3/4 NPT  |
| <b>AQT</b>  | Sub-base 1 NPT  |
| <b>AQU</b>  | Sub-base 1 1/4 NPT  |
| <b>AQV</b>  | Sub-base 1 1/2 NPT  |
| <b>G</b>    | Module without connecting thread, without sub-base        |
| <b>NG</b>   | Module without connecting thread, without sub-base (inch) |

|            |                                      |
|------------|--------------------------------------|
| <b>005</b> | <b>Performance Level</b>             |
| <b>C</b>   | Category 1, 1-channel to ISO 13849-1 |

|               |   |
|---------------|---|
| <b>006</b>    | <b>Supply voltage</b>   |
| <b>10V24P</b> | 24 V DC, 10 bar, M12 plug socket adapter (connection pattern to EN 60947-5-2) |
| <b>V110</b>   | 110 V AC (connection pattern to EN 175301)                                    |
| <b>V230</b>   | 230 V AC (connection pattern to EN 175301)                                    |
| <b>V24</b>    | 24 V DC (connection pattern to EN 175301)                                     |

|            |                 |
|------------|-----------------|
| <b>007</b> | <b>Silencer</b> |
|            | None            |
| <b>S</b>   | Silencer        |

|             |   |
|-------------|---|
| <b>008</b>  | <b>Pressure gauge alternatives</b>  |
|             | None  |
| <b>AG</b>   | MS pressure gauge   |
| <b>VS</b>   | Cover plate   |
| <b>A8</b>   | Adapter for EN pressure gauge 1/8, without pressure gauge                               |
| <b>A4</b>   | Adapter for EN pressure gauge 1/4, without pressure gauge                               |
| <b>RG</b>   | Integrated pressure gauge, red/green scale  |
| <b>AD7</b>  | Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/O   |
| <b>AD8</b>  | Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/C   |
| <b>AD9</b>  | Pressure sensor with switching display, M8 plug, window comparator, PNP, N/O            |
| <b>AD10</b> | Pressure sensor with operational status indicator, M8 plug, window comparator, PNP, N/C |

|            |   |
|------------|---|
| <b>009</b> | <b>Alternative pressure gauge scale</b> |
|            | MS pressure gauge                       |
| <b>PSI</b> | psi                                     |
| <b>BAR</b> | bar                                     |
| <b>MPA</b> | MPa                                     |


|            |   |
|------------|---|
| <b>010</b> | <b>Type of mounting</b>                                 |
| <b>WP</b>  | Mounting bracket basic design                           |
| <b>WPB</b> | Mounting bracket for large wall gap                     |
| <b>WPM</b> | Mounting bracket for hooking in service unit components |

|            |                          |
|------------|--------------------------|
| <b>011</b> | <b>Tamper protection</b> |
|            | None                     |
| <b>MK</b>  | Full                     |
| <b>MH</b>  | Without manual override  |

|            |                                   |
|------------|-----------------------------------|
| <b>012</b> | <b>Flow direction</b>             |
|            | Flow direction from left to right |
| <b>Z</b>   | Flow direction from right to left |




## Peripherals overview MS9-SV-C



## Mounting attachments and accessories

|      |                |  | Single device                          |                                      | Combination<br>Module without connect-<br>ing thread, without connect-<br>ing plate G, NG | → Page/<br>Internet |
|------|----------------|--|--|--------------------------------------|---|---------------------|
|      |                |  | With female thread<br>3/4, 1, N3/4, N1 | With connecting plate<br>AG.../AQ... |   |                     |
| [1]  | MS9-SV-C       | Soft-start/quick exhaust<br>valve                  | ■                                      | ■                                    | ■   | 41                  |
| [2]  | MS9-AG...      | Connecting plate SET                               | –                                      | ■                                    | ■   | ms9-ag              |
|      | MS9-AQ...      | Connecting plate SET                               | –                                      | ■                                    | ■   | ms9-aq              |
| [3]  | MS9-MV         | Module connector                                   | –                                      | –                                    | ■   | ms9-mv              |
| [4]  | MS9-WP         | Mounting bracket                                   | ■                                      | ■                                    | ■   | ms9-wp              |
| [5]  | MS9-WPB        | Mounting bracket                                   | ■                                      | ■                                    | ■   | ms9-wp              |
| [6]  | MS9-WPM        | Mounting bracket                                   | ■                                      | ■                                    | ■   | ms9-wp              |
| [7]  | U-1-B          | Silencer   | ■                                      | ■                                    | ■   | 41                  |
| [7]  | VS             | Cover plate  | ■                                      | ■                                    | ■   | 41                  |
| [9]  | AG/RG          | MS pressure gauge                                  | ■                                      | ■                                    | ■   | 41                  |
| [10] | AD7 ... AD10   | Pressure sensor with<br>switching status indicator | ■                                      | ■                                    | ■   | 41                  |
| [11] | NEBU-M8...-LE3 | Connecting cable                                   | ■                                      | ■                                    | ■   | 41                  |
| [12] | A4             | Adapter for EN pressure<br>gauge 1/4               | ■                                      | ■                                    | ■   | 41                  |
| [13] | MA             | Pressure gauge                                     | ■                                      | ■                                    | ■   | 41                  |
| [14] | MS9-SV-MH/MK   | Covering   | ■                                      | ■                                    | ■   | 41                  |

## Peripherals overview MS9-SV-C








**Note**  
 Additional accessories:  
 • Module connector for combination with size MS6, MS9 or MS12  
 → Internet: rmv

| Mounting attachments and accessories |            |                    | Single device                          |                                      | Combination  | → Page/<br>Internet |
|--------------------------------------|------------|--------------------|--|--------------------------------------|--|---------------------|
|                                      |            |                    | With female thread<br>3/4, 1, N3/4, N1 | With connecting plate<br>AG.../AQ... | Module without connect-<br>ing thread, without connect-<br>ing plate G, NG |                     |
| [1]                                  | MC-LD      | Illuminating seal  | ■                                      | ■                                    | ■  | 42                  |
| [2]                                  | KMC        | Connecting cable   | ■                                      | ■                                    | ■  | 42                  |
| [2]                                  | MSSD-C     | Plug socket        | ■                                      | ■                                    | ■  | 42                  |
| [4]                                  | NEBU-M12G5 | Connecting cable   | ■                                      | ■                                    | ■  | 42                  |
| [5]                                  | NEBU-M12W5 | Connecting cable   | ■                                      | ■                                    | ■  | 42                  |
| [6]                                  | SIE-GD     | Sensor socket      | ■                                      | ■                                    | ■  | 42                  |
| [7]                                  | SIE-WD     | Angled plug socket | ■                                      | ■                                    | ■  | 42                  |

## Datasheet MS9-SV-C

## Function



-  Flow rate  
8300 ... 16550 l/min
-  Temperature range  
0 ... +60°C
-  Operating pressure  
0.35 ... 1.6 MPa
-  [www.festo.com](http://www.festo.com)



Electropneumatic soft-start/quick exhaust valve for gradual pressurisation and quick exhausting of system components (single channel).

The main flow control valve in the end cap permits a slow build-up of output pressure p2. Once the output pressure p2 has reached the set pressure switchover point (switching pressure), the valve opens and the full operating pressure p1 is available at the output.

- Suitable for applications with a high flow rate in restricted spaces with medium safety requirements up to controller category 1, Performance Level c
- High volumetric flow rate for pressurisation and exhaust
- The filling flow rate can be set for gradual pressure build-up using a flow control valve
- Adjustable pressure switchover point
- Optional pressure sensor
- Optional cover for the control sections as tamper protection

## Safety data

|                        |   |
|------------------------|---|
| Conforms to            | EN ISO 13849-1  |
| Safety function        | Exhausting  |
| Performance Level (PL) | Exhausting: up to category 1, PL c  |
| Shock resistance       | Shock test with severity level 1 in accordance with FN 942017-5 and EN 60068-2-27 |
| Vibration resistance   | Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6  |

## General technical data

|                           |   |   |
|---------------------------|---|---|
| Pneumatic connection 1, 2 | Female thread   | G3/4, G1, 3/4 NPT or 1 NPT                      |
|                           | Connecting plate AG...  | G1/2, G3/4, G1, G1 1/4 or G1 1/2                |
|                           | Connecting plate AQ...  | 1/2 NPT, 3/4 NPT, 1 NPT, 1 1/4 NPT or 1 1/2 NPT |
|                           | Module without connecting thread/connecting plate G/NG  | –   |
| Pneumatic connection 3    | G1 (1 NPT) <sup>1)</sup>  |   |
| Actuation type            | Electrical  |   |
| Design                    | Piston spool  |   |
| Type of mounting          | Via accessories   |   |
|                           | In-line installation  |   |
| Mounting position         | Any   |   |
| Pressure indicator        | Via pressure sensor for indicating the output pressure and electrical output via switching status indicator |   |
|                           | Via pressure gauge for displaying the output pressure   |   |
|                           | Via pressure gauge with red/green scale for indicating the output pressure                                  |   |
|                           | Prepared for G1/4   |   |
| Valve function            | 3/2-way valve, closed, single solenoid  |   |
|                           | Soft-start function, adjustable   |   |
| Exhaust air function      | Cannot be throttled   |   |
| Reset method              | Mechanical spring   |   |
| Type of control           | Piloted   |   |
| Sealing principle         | Soft  |   |

1) Only with N3/4/N1/AQ.../NG without silencer S

† Note: This product conforms to ISO 1179-1 and ISO 228-1.

## Datasheet MS9-SV-C

| Electrical data              |                 |   |
|------------------------------|-----------------|---|
| Characteristic coil data     | V24             | 24 V DC: 8.4 W; permissible voltage fluctuations $\pm 10\%$   |
|                              | 10V24P          | 24 V DC: 2.7 W; permissible voltage fluctuations $\pm 10\%$   |
|                              | V110            | 110 V AC: 50/60 Hz; pick-up power 14.5 VA; holding power 10.5 VA; permissible voltage fluctuations $\pm 10\%$ |
|                              | V230            | 230 V AC: 50/60 Hz; pick-up power 14.5 VA; holding power 10.5 VA; permissible voltage fluctuations $\pm 10\%$ |
| Nominal operating voltage DC | [V]             | 110<br>230<br>24  |
| Electrical connection        | V24, V110, V230 | Plug, square design to EN 175301-803, type A  |
|                              | 10V24P          | M12x1, 4-pin, to IEC 61076-2-101, to DESINA   |
| Degree of protection         |                 | IP65 with plug socket   |
| Duty cycle                   | [%]             | 100   |

| Characteristic flow rate values                                    |               |       |                  |         |         |         |         |
|--|---------------|-------|------------------|---------|---------|---------|---------|
| Pneumatic connection   | Female thread |       | Connecting plate |         |         |         |         |
|  | 3/4/N3/4      | 1/N1  | AGD/AQR          | AGE/AQS | AGF/AQT | AGG/AQU | AGH/AQV |
| <b>Standard nominal flow rate <math>q_{nN}^{1)}</math> [l/min]</b> |               |       |                  |         |         |         |         |
| In main flow direction 1 $\rightarrow$ 2                           | 14150         | 16460 | 8300             | 13250   | 16340   | 16550   | 15910   |
| <b>Standard flow rate <math>q_n</math> [l/min]</b>                 |               |       |                  |         |         |         |         |
| Exhaust 6 $\rightarrow$ 0 bar with silencer S                      | 21450         | 20870 | 21720            | 20900   | 20370   | 19730   | 19850   |
| <b>C value [l/s*min]</b>   |               |       |                  |         |         |         |         |
| In main flow direction 1 $\rightarrow$ 2                           | 57.61         | 69.59 | 31.43            | 54.24   | 68.24   | 68.45   | 66.07   |
| In exhaust direction 2 $\rightarrow$ 3                             | 55.52         | 54.01 | 56.22            | 54.07   | 52.73   | 51.06   | 51.36   |
| <b>b value</b>   |               |       |                  |         |         |         |         |
| In main flow direction 1 $\rightarrow$ 2                           | 0.37          | 0.32  | 0.47             | 0.37    | 0.34    | 0.35    | 0.35    |
| In exhaust direction 2 $\rightarrow$ 3                             | 0.49          | 0.46  | 0.60             | 0.49    | 0.47    | 0.45    | 0.44    |

1) Measured at  $p_1 = 6$  bar and  $p_2 = 5$  bar,  $\Delta p = 1$  bar

| Operating and environmental conditions                      |         |  |                  |
|---|---------|--|------------------|
| Variance  |         | Coil coefficient   | Coil coefficient |
|   |         | V24  | 10V24P           |
| Operating pressure  | [MPa]   | 0.35 ... 1.6 (0.35 ... 1) <sup>2)</sup>  | 0.35 ... 1       |
|   | [bar]   | 3.5 ... 16 (3.5 ... 10) <sup>2)</sup>  | 3.5 ... 10       |
|   | [psi]   | 50.75 ... 232 (50.75 ... 145) <sup>2)</sup>  | 50.75 ... 145    |
| Operating medium  |         | Compressed air to ISO 8573-1:2010 [7:4:4]  |                  |
| Note on the operating/<br>pilot medium                      |         | Lubricated operation possible (in which case lubricated operation will always be required) |                  |
| Ambient temperature   | [°C]    | 0 ... +60 (0 ... +50) <sup>2)</sup>  |                  |
| Temperature of medium                                       | [°C]    | 0 ... +60 (0 ... +50) <sup>2)</sup>  |                  |
| Storage temperature   | [°C]    | 0 ... +60 (0 ... +50) <sup>2)</sup>  |                  |
| Corrosion resistance class CRC <sup>1)</sup>                |         | 2  |                  |
| Noise level <sup>3)</sup>                                   | [dB(A)] | 93 (with silencer S)   |                  |
| CE marking (see declaration of conformity <sup>4)</sup> )   |         | To EU EMC Directive<br>To EU Machinery Directive<br>To EU RoHS Directive                   |                  |
| UKCA marking (see declaration of conformity <sup>4)</sup> ) |         | To UK EMC regulations<br>To UK instructions for machines<br>To UK RoHS regulations         |                  |

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.

2) With pressure sensor AD...

3) Exhausting at 10 bar at a distance of 1 m.


4) Additional information: [www.festo.com/catalogue/MS-SV](http://www.festo.com/catalogue/MS-SV)  $\rightarrow$  Support/Downloads.

| Weight [g]                                     |      |
|--|------|
| Soft-start/quick exhaust valve                 | 2970 |
| Soft-start/quick exhaust valve with silencer S | 3200 |

## Datasheet MS9-SV-C

### Materials


Sectional view



Soft-start/quick exhaust valve

|                        |              |                    |
|------------------------|--------------|--------------------|
| [1]                    | Housing      | Die-cast aluminium |
| [2]                    | Piston spool | Brass              |
| -                      | Seals        | NBR                |
| Note on materials      |              | RoHS-compliant     |
| LABS (PWIS) conformity |              | VDMA24364-B1/B2-L  |

### Adjusting elements



[1] Screw for adjusting the pressure switchover point

[2] Flow control screw for adjusting the filling time

[3] Manual override at the soft-start/quick exhaust valve:  
 - detenting/self-resetting as soon as the solenoid coil or manual override at the pilot solenoid valve is actuated.

[4] Manual override at the pilot solenoid valve:  
 - non-detenting, actuation from above

### Dimensions – Basic version


Download CAD data → [www.festo.com](http://www.festo.com)

Module without connecting thread, without connecting plate G/NG, with cover plate VS

Supply voltage  
V24/V110/V230

Supply voltage 10V24P

With silencer S



- [1] Plug connection to EN 175301-803
- [2] Electrical connection to IEC 61076-2-101, M12x1 plug, 4-pin in accordance with DESINA
- [3] Manual override

→ Flow direction

| Type                            | B1 | B2 | B3  | D2    | D5                          | L1  | L2 | L3 | L4   | L5 | L6  |
|---------------------------------|----|----|-----|-------|-----------------------------|-----|----|----|------|----|-----|
| MS9-SV-G/NG-...-V24, V110, V230 | 90 | 45 | 109 | -     | G1<br>(1 NPT) <sup>1)</sup> | 200 | 83 | 23 | 36.4 | 12 | 189 |
| MS9-SV-G/NG-...-10V24P          |    |    |     | M12x1 |                             |     |    |    | 39.2 | 10 |     |

1) Only with N3/4/N1/AQ.../NG without silencer S


Datasheet MS9-SV-C

Dimensions – Connecting thread/connecting plate

Download CAD data → [www.festo.com](http://www.festo.com)

With female thread 3/4, 1, N3/4, N1

With connecting plate AG.../AQ...



[1] Retaining screw M6xmin. 90 to DIN 912 (not included in the scope of delivery) for wall mounting without mounting bracket

→ Flow direction

| Type        | B4 | B5  | B6   | B7  | B8  | D1        | D6 | D7  | L6 | T1 | ±ε |
|-------------|----|-----|------|-----|-----|-----------|----|-----|----|----|----|
| MS9-SV-3/4  | 90 | 104 | 91.5 | -   | -   | G3/4      | 11 | 6.5 | 66 | 6  | -  |
| MS9-SV-1    |    |     |      |     |     | G1        |    |     |    |    |    |
| MS9-SV-AGD  | -  | -   | -    | 112 | 132 | G1/2      | -  | -   | -  | -  | 30 |
| MS9-SV-AGE  |    |     |      |     | 132 | G3/4      |    |     |    |    | 36 |
| MS9-SV-AGF  |    |     |      |     | 142 | G1        |    |     |    |    | 41 |
| MS9-SV-AGG  |    |     |      |     | 162 | G1 1/4    |    |     |    |    | 50 |
| MS9-SV-AGH  |    |     |      |     | 176 | G1 1/2    |    |     |    |    | 55 |
| MS9-SV-N3/4 | 90 | 104 | 91.5 | -   | -   | 3/4 NPT   | 11 | 6.5 | 66 | 6  | -  |
| MS9-SV-N1   |    |     |      |     |     | 1 NPT     |    |     |    |    |    |
| MS9-SV-AQR  | -  | -   | -    | 112 | 132 | 1/2 NPT   | -  | -   | -  | -  | 30 |
| MS9-SV-AQS  |    |     |      |     | 132 | 3/4 NPT   |    |     |    |    | 36 |
| MS9-SV-AQT  |    |     |      |     | 142 | 1 NPT     |    |     |    |    | 41 |
| MS9-SV-AQU  |    |     |      |     | 162 | 1 1/4 NPT |    |     |    |    | 50 |
| MS9-SV-AQV  |    |     |      |     | 176 | 1 1/2 NPT |    |     |    |    | 55 |

† Note: This product conforms to ISO 1179-1 and ISO 228-1.


Datasheet MS9-SV-C

Dimensions – Pressure gauge/pressure gauge alternatives

Download CAD data → [www.festo.com](http://www.festo.com)

Integrated MS pressure gauge with standard scale AG or red/green scale RG

Adapter A4 for EN pressure gauge 1/4, without pressure gauge



| Type             | B2 | B3  | B9  | D3   |
|------------------|----|-----|-----|------|
| MS9-SV-...-AG/RG | 45 | 109 | –   | –    |
| MS9-SV-...-A4    |    | –   | 110 | G1/4 |


† Note: This product conforms to ISO 1179-1 and ISO 228-1.

Dimensions – Pressure gauge/pressure gauge alternatives

Download CAD data → [www.festo.com](http://www.festo.com)

Pressure sensor with switching status indicator AD7 ... AD10

Datasheets → Internet: sde5



[AD7]:  
SDE5-D10-O-...-P-M8 with 1x 3-pin M8 plug, threshold value comparator, 1 switching output PNP, N/O contact

[AD9]:  
SDE5-D10-O3-...-P-M8 with 1x 3-pin M8 plug, window comparator, 1 switching output PNP, N/O contact

[AD8]:  
SDE5-D10-C-...-P-M8 with 1x 3-pin M8 plug, threshold value comparator, 1 switching output PNP, N/C contact

[AD10]:  
SDE5-D10-C3-...-P-M8 with 1x 3-pin M8 plug, window comparator, 1 switching output PNP, N/C contact

| Type                           | B2 | B11 | D3 |
|--------------------------------|----|-----|----|
| MS9-SV-...-AD7, AD8, AD9, AD10 | 45 | 112 | M8 |

Ordering data

| Size               | With silencer |                     |
|--------------------|---------------|---------------------|
|                    | Part no.      | Type                |
| <b>Cover plate</b> |               |                     |
| MS9                | 570737        | MS9-SV-G-C-V24-S-VS |

## Ordering data – Modular product system MS9N-SV-C

| Ordering table  |   | Grid dimension | [mm] | 90  | Conditions   | Code           | Enter code |
|---|---|----------------|------|-----|--------------|----------------|------------|
| Module no.  |   | <b>562176</b>  |      |     |              |                |            |
| Series  | Standard  |                |      |     |              | <b>MS</b>      | MS         |
| Size  | 9   |                |      |     |              | <b>9</b>       | 9          |
| Function  | Soft-start/quick exhaust valve  |                |      |     |              | <b>-SV</b>     | -SV        |
| Pneumatic connection  | Female thread G3/4  |                |      |     |              | <b>-3/4</b>    |            |
|   | Female thread G1  |                |      |     |              | <b>-1</b>      |            |
|   | Connecting plate G1/2   |                |      |     |              | <b>-AGD</b>    |            |
|   | Connecting plate G3/4   |                |      |     |              | <b>-AGE</b>    |            |
|   | Connecting plate G1   |                |      |     |              | <b>-AGF</b>    |            |
|   | Connecting plate G1 1/4   |                |      |     |              | <b>-AGG</b>    |            |
|   | Connecting plate G1 1/2   |                |      |     |              | <b>-AGH</b>    |            |
|   | Female thread 3/4 NPT   |                |      |     |              | <b>-N3/4</b>   |            |
|   | Female thread 1 NPT   |                |      |     |              | <b>-N1</b>     |            |
|   | Connecting plate 1/2 NPT  |                |      |     |              | <b>-AQR</b>    |            |
|   | Connecting plate 3/4 NPT  |                |      |     |              | <b>-AQS</b>    |            |
|   | Connecting plate 1 NPT  |                |      |     |              | <b>-AQT</b>    |            |
|   | Connecting plate 1 1/4 NPT  |                |      |     |              | <b>-AQU</b>    |            |
|   | Connecting plate 1 1/2 NPT  |                |      |     |              | <b>-AQV</b>    |            |
|   | Module without connecting thread, without connecting plate  |                |      |     |              |                | <b>-G</b>  |
| Module without connecting thread, without connecting plate                          |   |                |      |     |              | <b>-NG</b>     |            |
| Performance Level   | Category 1, single-channel, to EN ISO 13849-1   |                |      |     |              | <b>-C</b>      | -C         |
| Supply voltage  | 24 V DC (plug pattern to EN 175301), 16 bar   |                |      |     |              | <b>-V24</b>    |            |
|   | 24 V DC, M12 to IEC 61076-2-101, 10 bar   |                |      |     |              | <b>-10V24P</b> |            |
|   | 110 V AC (plug pattern to EN 175301), 16 bar  |                |      |     |              | <b>-V110</b>   |            |
|   | 230 V AC (plug pattern to EN 175301), 16 bar  |                |      |     |              | <b>-V230</b>   |            |
| Silencer  | Silencer  |                |      |     |              | <b>-S</b>      |            |
| Pressure gauge/pressure gauge alternatives  | MS pressure gauge   |                |      |     |              | <b>-AG</b>     |            |
|   | Cover plate   |                |      |     |              | <b>-VS</b>     |            |
|   | Adapter for EN pressure gauge 1/8, without pressure gauge   |                |      |     |              | <b>-A8</b>     |            |
|   | Adapter for EN pressure gauge 1/4, without pressure gauge   |                |      |     |              | <b>-A4</b>     |            |
|   | Integrated pressure gauge, red/green scale  |                |      | [1] |              | <b>-RG</b>     |            |
|   | Pressure sensor with status indicator, M8 plug, threshold value comparator, PNP, N/O contact  |                |      | [2] |              | <b>-AD7</b>    |            |
|   | Pressure sensor with status indicator, plug M8, threshold value comparator, PNP, N/C contact  |                |      | [2] |              | <b>-AD8</b>    |            |
|   | Pressure sensor with status indicator, M8 plug, window comparator, PNP, N/O contact   |                |      | [2] |              | <b>-AD9</b>    |            |
| Pressure sensor with status indicator, M8 plug, window comparator, PNP, N/C contact |   |                | [2]  |     | <b>-AD10</b> |                |            |
| Alternative pressure gauge scale  | psi   |                |      | [3] |              | <b>-PSI</b>    |            |
|   | MPa   |                |      | [3] |              | <b>-MPA</b>    |            |
|   | bar   |                |      | [3] |              | <b>-BAR</b>    |            |
| Type of mounting  | Mounting bracket standard design  |                |      | [4] |              | <b>-WP</b>     |            |
|   | Mounting bracket for attaching service unit components  |                |      | [4] |              | <b>-WPM</b>    |            |
|   | Mounting bracket for large wall gap   |                |      | [4] |              | <b>-WPB</b>    |            |
| Tamper protection   | Without manual override (manual override at soft-start/quick exhaust valve blocked, setting screws open, manual override at pilot solenoid valve blocked) |                |      |     |              | <b>-MH</b>     |            |
|   | Complete (manual override at soft-start/quick exhaust valve blocked, setting screws blocked, manual override at pilot solenoid valve blocked)             |                |      |     |              | <b>-MK</b>     |            |
| Flow direction  | Flow direction from right to left   |                |      |     |              | <b>-Z</b>      |            |

[1] **RG** Not with alternative pressure gauge scale PSI.

PSI scale is only an auxiliary scale (inner scale), outer scale in bar

[2] **AD7, AD8, AD9, AD10** Measuring range max. 10 bar

[3] **PSI, MPA, BAR** Only in combination with pressure gauge AG or RG

[4] **WP, WPM, WPB** Not with pneumatic connection G, NG




## Accessories

### Multi-pin plug socket NECA

(Order code in the modular product system: MP1/MP3/MP5)

- for soft-start/quick exhaust valve  
MS6N-SV-E-10V24



| Technical data                      |                       |                                       |
|-------------------------------------|-----------------------|---------------------------------------|
| Type of mounting                    | Via through-hole      |                                       |
| Electrical connection 1             | Socket, sub-D, 9-pin  |                                       |
| Electrical connection 2             | Screw terminal, 9-pin |                                       |
| Operating voltage range [V DC]      | 21.6 ... 26.4         |                                       |
| Nominal operating voltage [V DC]    | 24                    |                                       |
| Acceptable current load at 40°C [A] | 1.0                   |                                       |
| Connection cross section            | [mm <sup>2</sup> ]    | 0.34 ... 1.0 without wire end sleeves |
|                                     | [mm <sup>2</sup> ]    | 0.34 ... 0.5 with wire end sleeves    |
| Permissible cable diameter [mm]     | 5.0 ... 10.0          |                                       |
| Degree of protection to IEC 60529   | IP65                  |                                       |

| Operating and environmental conditions       |                     |
|--|---------------------|
| Relative humidity                            | 95%, non-condensing |
| Ambient temperature [°C]                     | 0 ... +50           |
| Storage temperature [°C]                     | -20 ... +70         |
| Corrosion resistance class CRC <sup>1)</sup> | 2                   |

1) Corrosion resistance class CRC 2 to Festo standard FN 940070


Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.

| Materials |               |
|-----------|---------------|
| Housing   | Reinforced PA |
| Screws    | Steel         |
| Union nut | Brass         |
| Seals     | NBR           |

Accessories

Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



| B1 | H1 | L1 | L2   |
|----|----|----|------|
| 61 | 20 | 61 | 54.1 |

Ordering data

| Description        | Connection   | Weight [g] | Part no.      | Type                    |
|--------------------|--|------------|---------------|-------------------------|
| For MS6-SV-E-10V24 | Without cable, static enable signals (EN1 = 24 V, EN2 = 24 V)  | 60         | <b>548719</b> | <b>NECA-S1G9-P9-MP1</b> |
|                    | Without cable, static enable signals (EN1 = 0 V, EN2 = 24 V), cross-circuit detection possible                             | 60         | <b>552703</b> | <b>NECA-S1G9-P9-MP3</b> |
|                    | Without cable, static enable signals (EN1 = 0 V, EN2 = 24 V), galvanic isolation of enable signals from the supply voltage | 60         | <b>573695</b> | <b>NECA-S1G9-P9-MP5</b> |

## Accessories


### Silencer UOS-1

(Order code in the modular product system: S0)

- For soft-start/quick exhaust valve MS6-SV-D/E

### Silencer UOS-1-LF

- For soft-start/quick exhaust valve MS6-SV-D/E

 **Note**  
The space-saving silencer UOS-1-LF may only be used for applications with low exhaust rates. Pneumatic connection 2 at the soft-start/quick exhaust valve MS6-SV-D/E must be reduced to G1/4 by a connecting plate MS6-AGB.



UOS-1



UOS-1-LF



| Technical data                   |                  |
|----------------------------------|------------------|
| Pneumatic connection             | G1               |
| Design                           | Open silencer    |
| Type of mounting                 | With male thread |
| Mounting position                | Any              |
| Type of seal on screwed trunnion | No seal          |

| Operating and environmental conditions       |   |             |
|--|---|-------------|
| Operating pressure                           | [MPa]                                     | 0 ... 1     |
|  | [bar]                                     | 0 ... 10    |
| Operating medium                             | Compressed air to ISO 8573-1:2010 [-:-:-] |             |
| Ambient temperature                          | [°C]                                      | -10 ... +50 |
| Corrosion resistance class CRC <sup>1)</sup> | 2   |             |

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.

| Materials         |                         |                         |
|-------------------|-------------------------|-------------------------|
| Type              | UOS-1                   | UOS-1-LF                |
| Housing           | POM                     | Wrought aluminium alloy |
| Sleeve            | Wrought aluminium alloy | -                       |
| Silencer insert   | PU                      |                         |
| Note on materials | RoHS-compliant          |                         |

| Dimensions |   | Download CAD data → <a href="http://www.festo.com">www.festo.com</a>                 |  |
|------------|---|--|--|
| Type       | UOS-1   | UOS-1-LF   |  |
|            |  |  |  |

| Type     | D1 | D2 | L1    | L2   |
|----------|----|----|-------|------|
| UOS-1    | G1 | ∅  | 156.5 | 11.5 |
| UOS-1-LF | G1 | 55 | 72.2  | 13   |

| Ordering data |                       | Weight [g] | Part no. | Type     |
|---------------|-----------------------|------------|----------|----------|
| Description   | For MS6-SV-D/E        |            |          |          |
|               | For high exhaust rate | 200        | 552252   | UOS-1    |
|               | For low exhaust rate  | 157.9      | 1901207  | UOS-1-LF |


## Accessories

### Covering MS-SV-MH/MK

(Order code in the modular product system: MH/MK)

- For soft-start/quick exhaust valve MS6/9-SV-C

Note on materials: RoHS-compliant



MS6-SV-C-MK



MS9-SV-MK




MS9-SV-MH



| Ordering data |  | CRC <sup>1)</sup> | Part no.       | Type               |
|---------------|--|-------------------|----------------|--------------------|
| Description   |  |                   |                |                    |
| For MS6-SV-C  | Tamper protection for manual override at the soft-start/quick exhaust valve, flow control screw, setting screw for pressure switchover point and manual override at the pilot solenoid valve | 2                 | <b>8001479</b> | <b>MS6-SV-C-MK</b> |
| For MS9-SV-C  | Tamper protection for manual override at the soft-start/quick exhaust valve, flow control screw, setting screw for pressure switchover point and manual override at the pilot solenoid valve | 2                 | <b>1457669</b> | <b>MS9-SV-MK</b>   |
|               | Tamper protection for manual override at the soft-start/quick exhaust valve and manual override at the pilot solenoid valve  | 2                 | <b>1457670</b> | <b>MS9-SV-MH</b>   |


1) Corrosion resistance class CRC 2 to Festo standard FN 940070


Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.

## Accessories


| Ordering data – Silencer U...-B   |              |                      |  |               |                | Datasheets → Internet: u |
|---|--------------|----------------------|--|---------------|----------------|--------------------------|
|   | Description  | Pneumatic connection | Order code in the modular product system | Part no.      | Type           |                          |
|  | For MS6-SV-C | G3/4                 | S  | <b>6845</b>   | <b>U-3/4-B</b> |                          |
|   | For MS9-SV-C | G1                   | S  | <b>151990</b> | <b>U-1-B</b>   |                          |

| Ordering data – Proximity switch SMT  |              |                  |                            |                               |                  |  |               | Datasheets → Internet: smt       |
|---|--------------|------------------|----------------------------|-------------------------------|------------------|--|---------------|----------------------------------|
|   | Description  | Switching output | Switching element function | Electrical connection         | Cable length [m] | Order code in the modular product system | Part no.      | Type                             |
|  | For MS6-SV-D | PNP              | N/O                        | Cable with 1x M8 plug, 3-pin  | 0.3              | 2M8/S3                                   | <b>574334</b> | <b>SMT-8M-A-PS-24V-E-0.3-M8D</b> |
|   |              |                  |                            | Cable with 1x M12 plug, 3-pin | 0.3              | 2M12/S3                                  | <b>574337</b> | <b>SMT-8M-A-PS-24V-E-0.3-M12</b> |
|  | For MS6-SV-D | PNP              | N/O                        | Cable, 3-core                 | 5                | 20E/S3                                   | <b>574336</b> | <b>SMT-8M-A-PS-24V-E-5.0-OE</b>  |



| Ordering data – Plug socket MSSD  |                |                       |                                       |               |                      | Datasheets → Internet: mssd |
|---|----------------|-----------------------|---------------------------------------|---------------|----------------------|-----------------------------|
|   | Description    | Electrical connection | Type of mounting for cable connection | Part no.      | Type                 |                             |
|  | For MS6-SV-C/D | 3-pin                 | Clamping screws                       | <b>151687</b> | <b>MSSD-EB</b>       |                             |
|   |                | 4-pin                 | Insulation displacement technology    | <b>192745</b> | <b>MSSD-EB-S-M14</b> |                             |
|   |                | 3-pin                 | Clamping screws                       | <b>539712</b> | <b>MSSD-EB-M12</b>   |                             |
|   | For MS9-SV-C   | 3-pin                 | Clamping screws                       | <b>34583</b>  | <b>MSSD-C</b>        |                             |
|   |                | 4-pin                 | Insulation displacement technology    | <b>192748</b> | <b>MSSD-C-S-M16</b>  |                             |

| Ordering data – Plug socket with cable KMEB/Connecting cable KMC                    |                |                   |                       |                             |                        |                         | Datasheets → Internet: kmeb, kmc |                         |
|---|----------------|-------------------|-----------------------|-----------------------------|------------------------|-------------------------|----------------------------------|-------------------------|
|   | Description    | Operating voltage | Electrical connection | Switching status indication | Cable length [m]       | Part no.                | Type                             |                         |
|  | For MS6-SV-C/D | 24 V DC           | 2-pin                 | LED                         | 2.5                    | <b>547268</b>           | <b>KMEB-3-24-2.5-LED</b>         |                         |
|   |                |                   |                       | –                           | 5                      | <b>547269</b>           | <b>KMEB-3-24-5-LED</b>           |                         |
|   |                |                   |                       | –                           | 2.5                    | <b>547270</b>           | <b>KMEB-3-24-2.5</b>             |                         |
|   |                |                   | –                     | 5                           | <b>547271</b>          | <b>KMEB-3-24-5</b>      |                                  |                         |
|   |                |                   | 3-pin                 | LED                         | 2.5                    | <b>151688</b>           | <b>KMEB-1-24-2.5-LED</b>         |                         |
|   |                |                   |                       | –                           | 5                      | <b>151689</b>           | <b>KMEB-1-24-5-LED</b>           |                         |
|   |                | –                 |                       | 10                          | <b>193457</b>          | <b>KMEB-1-24-10-LED</b> |                                  |                         |
|   |                | 230 V AC          | 3-pin                 | –                           | 2.5                    | <b>151690</b>           | <b>KMEB-1-230AC-2.5</b>          |                         |
|   |                |                   |                       |                             | 5                      | <b>151691</b>           | <b>KMEB-1-230AC-5</b>            |                         |
|   |                |                   |                       |                             | 24 V DC                | 3-pin                   | LED                              | 2.5                     |
| 5   | <b>30933</b>   |                   |                       |                             |                        |                         |                                  | <b>KMC-1-24DC-5-LED</b> |
| 230 V AC  | 3-pin          | –                 | 10                    | <b>193459</b>               | <b>KMC-1-24-10-LED</b> |                         |                                  |                         |
|   |                |                   | 2.5                   | <b>30932</b>                | <b>KMC-1-230AC-2.5</b> |                         |                                  |                         |
|   |                |                   |                       | 5                           | <b>30934</b>           | <b>KMC-1-230AC-5</b>    |                                  |                         |



## Accessories

| Ordering data – Illuminating seal MEB-LD/MC-LD                                   |   |                         |  |          | Datasheets → Internet: meb, mc |  |
|--|---|-------------------------|--|----------|--------------------------------|--|
|  | Description   | Operating voltage range |  | Part no. | Type                           |  |
|  | For plug socket with cable KMEB and plug socket MSSD-EB | 12 ... 24 V DC          |  | 151717   | MEB-LD-12-24DC                 |  |
|  |   | 230 V DC/AC ±10%        |  | 151718   | MEB-LD-230AC                   |  |
|  | For connecting cable KMC and plug socket MSSD-C         | 12 ... 24 V DC          |  | 19145    | MC-LD-12-24DC                  |  |
|  |   | 230 V DC/AC ±10%        |  | 19146    | MC-LD-230AC                    |  |


  

| Ordering data – Connecting cable NEBU-M8   |                       |                 |                  |          | Datasheets → Internet: nebu |  |
|--|-----------------------|-----------------|------------------|----------|-----------------------------|--|
|  | Electrical connection | Number of wires | Cable length [m] | Part no. | Type                        |  |
|  | M8x1, straight socket | 3               | 2.5              | 541333   | NEBU-M8G3-K-2.5-LE3         |  |
|  |                       |                 | 5                | 541334   | NEBU-M8G3-K-5-LE3           |  |
|  | M8x1, angled socket   | 3               | 2.5              | 541338   | NEBU-M8W3-K-2.5-LE3         |  |
|  |                       |                 | 5                | 541341   | NEBU-M8W3-K-5-LE3           |  |


  

| Ordering data – Connecting cable NEBU-M12   |                        |                 |                  |          | Datasheets → Internet: nebu |  |
|---|------------------------|-----------------|------------------|----------|-----------------------------|--|
|   | Electrical connection  | Number of wires | Cable length [m] | Part no. | Type                        |  |
|   | M12x1, straight socket | 4               | 2.5              | 550326   | NEBU-M12G5-K-2.5-LE4        |  |
|   |                        |                 | 5                | 541328   | NEBU-M12G5-K-5-LE4          |  |
|  | M12x1, angled socket   | 4               | 2.5              | 550325   | NEBU-M12W5-K-2.5-LE4        |  |
|   |                        |                 | 5                | 541329   | NEBU-M12W5-K-5-LE4          |  |


  

| Ordering data – Sensor socket SIE-GD   |                       |  |  | Datasheets → Internet: sie-gd |        |
|--|-----------------------|--|--|-------------------------------|--------|
|  | Electrical connection |  |  | Part no.                      | Type   |
|  | M12x1, 4-pin          |  |  | 18494                         | SIE-GD |

| Ordering data – Angled plug socket SIE-WD  |                       |  |  | Datasheets → Internet: sie-wd |           |
|--|-----------------------|--|--|-------------------------------|-----------|
|  | Electrical connection |  |  | Part no.                      | Type      |
|  | M12x1, 4-pin          |  |  | 12956                         | SIE-WD-TR |

| Ordering data – Pressure gauge MA  |  |                      |               |           |                    |                           |
|--|--|----------------------|---------------|-----------|--------------------|---------------------------|
|  | Nominal size   | Pneumatic connection | Display range |           | Part no.           | Type                      |
|  |  |                      | [bar]         | [psi]     |                    |                           |
|  | <b>Pressure gauge MA, EN 837-1</b>                       |                      |               |           |                    | Datasheets → Internet: ma |
|  | 40   | R1/4                 | 0 ... 16      | 0 ... 232 | 187080             | MA-40-16-R1/4-EN          |
|  |  | G1/4                 | 0 ... 16      | 0 ... 232 | 183901             | MA-40-16-G1/4-EN          |
|  | <b>Pressure gauge MA, EN 837-1, with red/green range</b> |                      |               |           |                    | Datasheets → Internet: ma |
| 50   | R1/4   | 0 ... 16             | –             | 525729    | MA-50-16-R1/4-E-RG |                           |

# Festo - Your Partner in Automation



**1 Festo Inc.**  
5300 Explorer Drive  
Mississauga, ON L4W 5G4  
Canada

**Festo Customer Interaction Center**  
Tel: 1 877 463 3786  
Fax: 1 877 393 3786  
Email: [customer.service.ca@festo.com](mailto:customer.service.ca@festo.com)

**2 Festo Pneumatic**  
Av. Ceylán 3,  
Col. Tequesquináhuac  
54020 Tlalneantla,  
Estado de México

**Multinational Contact Center**  
01 800 337 8669  
[ventas.mexico@festo.com](mailto:ventas.mexico@festo.com)

**3 Festo Corporation**  
1377 Motor Parkway  
Suite 310  
Islandia, NY 11749

**Festo Customer Interaction Center**  
1 800 993 3786  
1 800 963 3786  
[customer.service.us@festo.com](mailto:customer.service.us@festo.com)

**4 Regional Service Center**  
7777 Columbia Road  
Mason, OH 45040

Connect with us



[www.festo.com/socialmedia](http://www.festo.com/socialmedia)



[www.festo.com](http://www.festo.com)

Subject to change