


# Installation system CPI

**FESTO**



## Key features



### Key features

#### Innovative

- Complete concept for decentralised machine and system structure; centralised and decentralised installation is possible in combination with the CPX terminal
- Decentralised pneumatic components and sensors for fast processes
- Centralised electric components for fieldbus and common power supply
- Flexible configuration of the individual CP strings
- Choice of valve terminal sizes for optimum pneumatic control loop systems
- Performance data as for the CP system with the addition of the comprehensive diagnostic capabilities of the CPX terminal

#### Sturdy

- Electrical accessories to IP65
- Proven valve terminals CPV (compact), MPA-S (sturdy, modular)
- Electrical input and output modules in metal housing or compact in encapsulated plastic housing
- Sturdy connection technology M12, alternatively M8

#### Versatile

- A number of CP interfaces can be combined under one bus node
- Four CP strings up to 10 m in length (radius) facilitate optimum decentralisation
- Max. 32 inputs and 32 outputs/valves per string
- Available valves:
  - Valve terminal CPV-SC, max. 170 l/min flow rate
  - Valve terminal MPA-S, max. 700 l/min flow rate
  - Valve terminal CPV, max. 1600 l/min flow rate
  - Valve terminals with I-Port interface (VTUG, CPV, MPA-L, VTUB-12, VTOC)
- Input modules with 8 ... 32 inputs and output modules with 4 ... 8 outputs, each with or without additional power supply

#### Operational safety

- Sturdy modules and accessories
- Ready-to-install system including CP cable (hybrid cable for data and power)
- Short circuit-proof connections with reverse polarity protection
- Valves with separate load voltage supply
- All modules equipped with local diagnostics and status LEDs
- Diagnostics of each CP string via controller/fieldbus
- Self-learning system (save button) for current configuration
- Easy replacement of modules at any time

## Key features

### Installation system CPI

The CPI system is capable of meeting the completely contrasting requirements created by the difference between extensive decentralised modularisation and electrical installation.

High-speed machines require short cycle times and short pneumatic tubing. The valves must be mounted close to the cylinders. The CPI system was developed to meet these requirements without having to wire each valve individually.

The system integrates the modular valve terminal MPA-S with internal communication system, valve terminals with integrated sub-base CPV that are suitable for operating small pneumatic drives, and various input/output modules in a single installation concept.

All CP valve terminals and CP modules are connected using a ready-to-install CP cable, and are attached to the CP interface. 4 modules, for example one CPV valve terminal and one to three CP input modules, make up an installation string that ends at the CP interface.


#### Scope of services:

- Max. 4 installation strings per CP interface
- Max. 10 metre line length per string (radius)
- Max. 4 CP modules per string
- Max. 32 inputs and max. 32 outputs per string

The number of CP modules that can be connected and the number of inputs/outputs is dependent on the type of CP module and CP interface.

The maximum configuration (4 modules per string, 32 inputs/outputs) is only possible in combination with the CPX terminal and CP modules with CPI functionality.


The CP interface is the central connection point for the valve power supply and the sensor supply. The power supply for the sensors connected to the input modules is separate from the load voltage supply of the valves.



## Key features


### Node types

Fieldbus



CPX with CP interface  
CPX-...

Valve terminal




with CP string extension  
CPV, CPV-SC, MPA-S

## Peripherals overview

### Integration of the installation system CPI in various connection concepts

#### Centralised pneumatic connection (valve terminal)




##### Advantages

- Pneumatic multiple connector plate
- Less tubing required than with individual valves
- Common valve air supply
- Central positioning
- Material, weight and cost savings

##### Disadvantages

- Only effective with a large number of closely spaced actuators
- Heavier than an individual valve (lower overall weight than the same number of individual valves), which may make mounting on moving systems or in very cramped installation spaces difficult
- Longer tube lengths are occasionally required, ruling out the possibility of optimum pneumatic performance

#### Decentralised pneumatic connection (individual valve/valve on individual sub-base)




##### Advantages

- Can be positioned directly at the actuator, can even be integrated
- Short tubing length to the actuator enables short switching times
- Optimum pneumatic timing and performance possible

##### Disadvantages

- Air supply per valve requires more tubing
- Serial electrical links not advisable/possible
- More complex electrical installation

#### Centralised electrical connection (multi-pin/fieldbus connection/standalone mini control system)



##### Advantages

- Internal electrical links requires less cabling
- Increased transparency
- Material, weight and cost savings
- Ideal for connecting a large number of closely spaced valves


##### Disadvantages

- Not suitable for individual, more widely separated applications due to the more complex cabling
- More complex individual components (cables, fieldbus modules)

## Peripherals overview

### Integration of the installation system CPI in various connection concepts

Decentralised electrical connection (CPI system/individual valve/valve on individual sub-base/valve manifold assembly)




#### Advantages

- CPI system with reduced installation effort for groups of actuators/sensors
- Different levels of complexity with widely separated individual components
- Easy replacement of components during servicing
- Optimum pneumatic timing and performance possible

#### Disadvantages

- Limited spatial expansion possible (CPI system up to 10 m, AS-Interface up to 100 m)
- High installation costs

Combined centralised and decentralised electrical connection (valve terminal with CP interface/output module)



#### Advantages

- Scalable to different requirements within a system
- One control interface in the system, reduces installation complexity with closely and widely spaced actuators
- Enables an optimum electrical and pneumatic control chain

#### Disadvantages

- Application must at least partially meet the requirements of a centralised connection

### Connecting the installation system CPI to a higher-level controller

Bus node/Industrial Ethernet

Different bus nodes are used for integration in the control systems of various manufacturers.

The CPI system can therefore be operated via more than 90% of the most commonly used bus systems.

- PROFIBUS
- DeviceNet
- CANopen
- CC-LINK
- EtherNet/IP
- PROFINET
- POWERLINK
- EtherCAT
- Sercos III

Control block

The optional Front End Controller CPX-CEC permits simultaneous access via Ethernet and an integrated web server, as well as autonomous pre-processing.


- Ethernet
- TCP/IP
- Web

## Peripherals overview

### Connecting the installation system CPI to a higher-level controller

#### Overview

CPX bus node/control block



CPX CP interface

#### Bus protocol/bus node

##### DeviceNet

FB11

#### Special features

- Up to 512 digital inputs/outputs
- 18 analogue inputs/outputs

##### PROFIBUS DP

FB13

- Up to 512 digital inputs/outputs
- 18 analogue inputs/outputs

##### CANopen

FB14

- Up to 64 digital inputs and 64 digital outputs
- 8 analogue inputs and 8 analogue outputs

##### CC-LINK

FB23-24

- Up to 512 digital inputs/outputs
- 32 analogue inputs/outputs

##### EtherNet/IP

FB36

- Up to 128 digital inputs/outputs
- 8 analogue inputs/outputs

##### PROFINET

FB43

- Up to 512 digital inputs/outputs
- 32 analogue inputs/outputs

FB44

FB45

##### EtherCAT

FB37

- Up to 512 digital inputs/outputs
- 32 analogue inputs/outputs

##### POWERLINK

FB40

- Up to 512 digital inputs/outputs
- 32 analogue inputs/outputs

##### Sercos III

FB39

- Up to 512 digital inputs/outputs
- 32 analogue inputs/outputs

The precise technical data and specifications for CPX can be found online at:

→ Internet: [cpx](http://cpx)

## Peripherals overview

### Connecting modules in the installation system CPI

CP interface within the context of the CPX terminal

Using the CP interface as a module of the CPX terminal makes it easier to progress from the CP system to the CPI system.


All CP modules are both downwards and upwards compatible and can therefore be used in the CP system and in the CPI system.

This extension has doubled the scalability and range of CP modules that can be used:

- 4 CP strings
- Up to 4 modules per string
- Up to 32 inputs and outputs per CP string


An added advantage of the CPI system is its extremely user-friendly access options via the CPX bus node and the CPX-CEC:

- Data preprocessing
- Diagnostics via software
- Reading out of status information
- Display via permanently installed or mobile unit
- Remote maintenance with CPX-CEC and Ethernet connection






## Connection options

Fieldbus Direct			
Special feature	Application	Characteristics of Fieldbus Direct	
<p>The Fieldbus Direct product range is the most compact way of connecting valves to a fieldbus. The bus node is directly integrated in the electrical actuation of the valve terminal and therefore takes up only a minimal amount of space.</p>	<p>Fieldbus Direct is a system for the compact connection of a valve terminal to different bus standards. The CP string extension option enables the functions and components of the CPI installation system to be used.</p>	<ul style="list-style-type: none"> <li>Extremely compact and space-saving design</li> <li>Low-cost solution for connecting a small number of valves to the fieldbus</li> <li>Direct front-end integration with a high degree of protection IP65</li> <li>Comprehensive diagnostics and condition monitoring</li> </ul>	<p> <b>Note</b></p> <p>Detailed description of the range of functions and combination options of CPV valves  → Internet: cpv (valve terminal CPV)</p>
Fieldbus Direct and CP string extension			
<p>The optional string extension allows a further valve terminal and I/O modules to be connected to the Fieldbus Direct bus node:</p> <ul style="list-style-type: none"> <li>A CP string of the CP system is integrated in the bus node as an extension.</li> <li>Various input and output modules as well as valve terminals can be connected.</li> </ul>	<p>The maximum length of the CP string extension is 10 metres, which means that the extension modules can be mounted directly on site. All of the required electrical signals including load current supply are transmitted via the CP cable, which in turn means that no further installation is needed on the extension module.</p>	<p>The CP string interface offers:</p> <ul style="list-style-type: none"> <li>Max. 32 input signals</li> <li>Max. 32 output signals for output modules 24 V DC or solenoid coils</li> <li>Logic and sensor supply for the input modules</li> </ul>	<ul style="list-style-type: none"> <li>Load voltage supply for the valve terminal</li> <li>Logic supply for the output module</li> </ul>

## Connection options

### Fieldbus Direct with CP string extension

CPV valve terminal




- 4 to 8 valve positions
- DeviceNet

- 4 to 16 solenoid coils

More information

→ Internet: [cpv](#)

### Compact vision system SBOC-Q/SBOI-Q with CP interface



The compact vision system SBOx-Q can be integrated into a Festo CPI network. In this case it functions like a binary module with 16 inputs and 16 outputs.

- Address requirement: 16 digital inputs/outputs
- CPI connection


More information

→ Internet: [sboc-q](#), [sboi-q](#)


## Connection options

### Connecting inputs and outputs in the installation system CPI

#### CP connecting cable



KVI-CP-3-...



**Note**

The total length of all CP cables in a CP string must not exceed 10 m.

- Pre-assembled cables for connecting the CP modules
- Lengths from 0.25 to 8 metres
- M9 plug/socket, 5-pin
- Straight/angled version in any combination

More information  
→ Internet: [kvi-cp](#)

#### CP input/output modules in sturdy, universal design or as valve terminal

Input and output modules with different electrical interfaces are available for connecting sensors and actuators:


- M12-5POL
- M8-3POL
- M8-4POL

The maximum number of inputs/outputs that can be connected to the individual modules can vary depending on the application. The following module sizes are available:

- Input modules with 8, 16 or 32 channels
- Output modules with 4 or 8 channels
- CPV with 4, 6 or 8 valve slices (max. 16 valves)
- MPA-S with 2 ... 32 valves

### Valve terminals with CP interface

#### CPV valve terminal




CPV10  
CPV14  
CPV18

- Max. 16 valves in 8 valve slices
- Highly compact and space-saving
- Width 10, 14, 18 mm
- Nominal flow rate  
400/800/1600 l/min
- CPV10 and CPV14 with CPI functionality
- CPV18 with CP functionality

More information  
→ Internet: [cpv](#)  
(valve terminal CPV)

#### Valve terminal MPA-S




MPA1  
MPA14  
MPA2

- Max. 32 valves (32 solenoid coils, 16 valve positions)
- Modular and versatile
- Width 10, 14, 20 mm
- Nominal flow rate  
360/550/700 l/min
- CPI functionality

More information  
→ Internet: [mpa-s](#)  
(valve terminal MPA-S)

#### Valve terminal MPA-S




CPV-SC

- Max. 16 valves
- Extremely compact
- Width 10 mm
- Nominal flow rate 170 l/min
- CPI functionality

More information  
→ Internet: [cpv-sc](#)  
(valve terminal CPV-SC)

#### Valve terminal with I-Port interface



Valve terminals:

- VTOC
- VTUB-12
- CPV
- MPA-L
- VTUG

Flow rate

- 10 l/min
- 400 l/min
- 400/800 l/min
- 360/670/700 l/min
- 130 ... 1200 l/min

More information

- Internet: [vtoc](#)
- Internet: [vtub-12](#)
- Internet: [cpv](#)
- Internet: [mpal](#)
- Internet: [vtug](#)
- Internet: [cteu](#)

## Key features – Input/output modules

### Connecting inputs and outputs in the installation system CPI


Special features of the CP I/O modules in sturdy design

The sturdy CP I/O modules have a highly resistant aluminium housing and their internal electronic components can be repaired or replaced.

CP-E...Z or output modules have a separate load voltage supply, which means less load on the CP interface and CP cable and more power for the connected consuming devices.


This also makes it easier to disconnect the consuming devices separately.

### CP input modules in sturdy design




CP-E16-M12x2-5POL

- 16 inputs 24 V DC
- Signal status indication via 16 LEDs
- Operating status indication
- CP functionality
- M12 plug, double allocation
- 1x M9 CP connection
- PNP/NPN, IP65



CP-E16-M8


- 16 inputs 24 V DC
- Signal status indication via 16 LEDs
- Operating status indication
- CP functionality
- M8 plug, single allocation
- 1x M9 CP connection
- PNP/NPN, IP65



CP-E16-M8-Z

- 16 inputs 24 V DC
- Signal status indication via 16 LEDs
- Operating status indication
- CP functionality
- Galvanic isolation through additional power supply
- M8 plug, single allocation
- 1x M9 CP connection
- Separate sensor supply
- PNP/NPN, IP65

### CP output modules in a sturdy design



CP-A08-M12-5POL

- 8 outputs 24 V DC
- Output signal display via 8 LEDs
- Operating status indication
- M12 plug, single allocation
- CP functionality
- 2x M9 CP connection
- Separate load voltage
- Outputs resistant to overloads and short circuits
- PNP, IP65

## Key features – Input/output modules

## Connecting inputs and outputs in the installation system CPI

Special features of the CP I/O modules in economical design

In addition to the sturdy CP I/O modules, there are also the economical modules with a greater number of inputs/outputs.

The economical CP modules feature a compact design, coupled with a large number of inputs/outputs. The modules can be used in combination with the following valve terminals:


- CPV, MPA-S, CPV-SC

**Application:**

- Same function, configuration and commissioning as sturdy CP modules
- Integrated H-rail mounting and earthing plate
- Centrally placed status and diagnostic LEDs
- The economical CP modules and the other CP modules can be operated together on a string

- The maximum number of modules per CP string is as follows:
  - CPI system: max. 4 modules or max. 32 inputs and 32 outputs
  - CP system: one valve terminal/output module and one input module


## CP input modules in economical design



CP-E16-M12-EL

- 16 inputs 24 V DC
- Signal status indication via 16 LEDs
- Operating status indication (per module and per group of 4 inputs)
- CPI functionality

- 8x M12 plug, 5-pin, double allocation
- 2x M9 CP connection
- PNP, IP65




CP-E16-M8-EL

- 16 inputs 24 V DC
- Signal status indication via 16 LEDs
- Operating status indication (per module and per group of 4 inputs)
- CPI functionality

- 16x M8 plug, 3-pin, single allocation
- 2x M9 CP connection
- PNP, IP65

## CP output modules in economical design



CP-A08-M12-EL-Z


- 8 outputs 24 V DC
- Signal status indication via 4 LEDs
- Operating status indication (per module and per channel/output)
- CPI functionality

- 8x M12 plug, 5-pin, double allocation
- 2x M9 CP connection
- Outputs resistant to overloads and short circuits
- PNP, IP65

## Key features – Mounting options

### H-rail mounting

CP interface



The H-rail mounting is part of the rear profile of the CPX interlinking blocks. The CPX terminal can be attached to the H-rail using the H-rail mounting kit.


The CPX terminal is first hooked onto the H-rail (see arrow 1), then swivelled onto the H-rail and secured in place with the clamping element (see arrow 2).

The following mounting kit is required for H-rail mounting (plus mounting kit for optionally mounted valves):

- CPX-CPA-BG-NRH

This enables mounting on H-rails to EN 60715.

### Economical CP modules



The H-rail mounting is impressed in the reverse profile of the economical CP modules. The modules can be attached to the H-rail using the H-rail mounting kit.


The module is first hooked onto the H-rail (see arrow 1), then swivelled onto the H-rail and secured in place with the clamping element (see arrow 2).

The scope of delivery includes the following mounting kit for H-rail mounting:

- CP-EL-HS

This enables mounting on H-rails to EN 60715.

### Sturdy CP modules



For the CP modules there is a mounting kit that can be used on an H-rail.

The following mounting kit is needed for H-rail mounting:


- CP-TS-HS35

This enables mounting on H-rails to EN 60715.

## Key features – Mounting options

### Wall mounting

CP modules



The CP modules (with screws up to 4 mm in diameter) can be mounted on even surfaces in almost any position using the mounting holes.

## Key features – Inscription system


### Inscription system

All CP modules have holders for inscription labels.

Inscription labels/label holders are not included in the scope of delivery and can be ordered separately.

The labels can be pre-assembled on request.


### Sturdy CP modules



The sturdy CP modules have two slots in which the inscription labels IBS-6x10 (part no. 18576) can be fitted. At least one inscription label can be fitted per connection.

The IBS-6x10 are plastic clips that can be printed on, written on or affixed with labels.

### Economical CP modules



The economical CP modules have six fixtures on the side, each for one inscription label holder ASCF-H-E2 (part no. 547473).

The ASCF-H-E2 are transparent, hinged inscription label holders for holding premade paper inscription labels. The label can be read when the label holder is opened out.






## Key features – Power supply

### Power supply concept of the CPX terminal

Circuit diagram for M18 power supply/system supply (example)



The use of decentralised devices on the fieldbus – particularly with a high degree of protection for direct machine mounting – demands a flexible power supply concept. The CPX terminal makes it easier to connect all voltages via one socket.

A distinction is made between supply for

- electronics and sensors/inputs
- valves
- actuators/outputs

Selectable connection technology:

- M18
- 7/8"
- AIDA push-pull



#### Note

The CP interface connects the 0 V of the power supply for the electronics/inputs and the valves.

To prevent overloads, the power must therefore be supplied using just one power supply module or using power supply units with a common PEN conductor.

### Interlinking blocks

Many applications require the voltage to be segmented into zones. This applies in particular to the separate disconnection of connected actuators (solenoid coils/outputs).

The separation of voltages for valves and the creation of different voltage segments for electrical outputs and sensors are supported by the different interlinking blocks of the CPX terminal:

- With system supply
- Without power supply
- With additional power for electrical outputs
- With additional supply for valves

The supply voltages are supplied using a

- 4-pin M18 plug
- 4-pin 7/8" plug
- 5-pin 7/8" plug
- AIDA push-pull, 5-pin



#### Note

The max. current is limited to 12 A with the 7/8" system supply. When using a conventional pre-assembled cable, the max. current is limited to 8 A.

## Key features – Diagnostics

### General limits

#### System supply

The system supply provides the internal voltage for the entire CPX system with

- max. 16 A for electronics and sensors/inputs
- max. 16 A for actuators/outputs and valves

#### CP interface

The CP interface and the CP modules connected to the CP interface get their operating voltage from the connection for electronics and sensors/inputs.

The operating voltage for the sensors/actuators connected to the CP modules is supplied from the voltage for valves.

The CP interface supplies the connected CP modules with

- max. 1.6 A per CP string

### Diagnostics

#### General

A comprehensive diagnostic function is available for each string.

The diagnostic information can either be detected via the LEDs on the module and then read out and evaluated via the controller software (non-field-bus-specific) or displayed directly on the CPX terminal via the diagnostic interface and then evaluated and processed.

#### Diagnostics via LEDs

- Error in bus communication
- POWER, power supply indicator for internal electronics
- POWER V, load voltage indicator for valves
- 0 ... 3, CP string allocation changed or interrupted


There are also bus-specific LED displays.

#### Diagnostics via control program

- Configuration error
- Bus error
- Operating voltage failure
- Falling below voltage tolerance (valves)
- Short circuit in sensor voltage supply

- Operating voltage failure at the output modules
- Short circuit/overload at the output modules
- Connection to one or more CP modules interrupted (valve terminal, input/output modules)

#### Diagnostics via CPX terminal




- [1] Diagnostics via controller/bus node
- [2] Bus-specific LEDs
- [3] String diagnostics via LED on the CP interface
- [4] Diagnostics via CP string
- [5] Diagnostics via LED on CP module
- [6] Status indicator on the CP module

## Key features – CP interface


### Diagnostics

Diagnostics via CP bus node



- [1] Diagnostics via fieldbus
- [2] Bus-specific LEDs
- [3] String diagnostics via LED on the bus node
- [4] Diagnostics via LED on CP module
- [5] Diagnostics via CP string
- [6] Status indicator on the CP module

### Diagnostic LEDs on the CP modules



- [1] Status LED  
CP communication  
(PS, green)
- [2] Status LED (module) for short circuit/overload of sensor supply (red)
- [3] Status LEDs for inputs (status indication, green)
- [4] Status LED (group, only with CP-E16-...-EL) for short circuit/overload of sensor supply (red)

In addition to the status indication per module and per individual channel/input, the economical modules with 16 inputs additionally have a status indication for a group of four inputs. The following inputs are combined into groups of four:

- 0 ... 3
- 4 ... 7
- 8 ... 11
- 12 ... 15

### Parameterisation

The addresses to the individual actuators/outputs or sensors/inputs, which are connected to the CP modules, are allocated in accordance with the bus node or CPX-CEC used. Address allocation is performed in accordance with the following rules:

- One CP interface provides four strings with a total of 128 input and 128 output addresses.
- A used string occupies 32 input and 32 output addresses.
- The addresses are permanently allocated to the strings and CP modules in ascending order.
- Unused address space remains reserved for future extensions.

The CP interface checks the configuration of the connected modules each time the system is switched on and during operation. If a deviation from the saved configuration is detected, an appropriate message is output via the controller software and displayed via LED.

The configuration detected is stored by pressing the Save button (after the operating voltage is switched on at the CP interface).

The configuration is stored each time the CP interface is switched off and back on. There is an option to replace a connected CP module with an identical module during operation. Removal of more than one module from the current configuration will be detected as an error; the address spaces of these modules will no longer be actuated.

## Selection aid


System selection aid					
	Modules per string	Outputs/inputs per string	Modules with CP functionality	Modules with CPI functionality	String length [m]
CP system	2	16/16	0 ... 1 input module 0 ... 1 output module	0 ... 1 input module 0 ... 1 output module	0 ... 10
CPI system	4	32/32	0 ... 1 input module 0 ... 1 output module	0 ... 4 input modules 0 ... 4 output modules	0 ... 10

Module selection aid							
	Functionality		Additional power supply	Address requirement		Max. current consumption [A]	→ Page/Internet
	CP	CPI		Inputs	Outputs		
<b>Input modules</b>							
CP-E16-M8	■	–	–	16	–	0.54	26
CP-E16-M12x2-5POL	■	–	–	16	–	0.59	26
CP-E16-M8-Z	■	–	■	16	–	1.04	27
CP-E16-M8-EL	■	■	–	16	–	0.7	32
CP-E16-M12-EL	■	■	–	16	–	0.7	32
<b>Output modules</b>							
CP-A08-M12-5POL	■	–	■	–	8	2.09	43
CP-A08-M12-EL-Z	■	■	■	–	8	4	46
<b>Connecting cables</b>							
KVI-CP-3-...	■	■	–	–	–	1.6	kvi-cp
<b>Valve terminals</b>							
CPV10-FB-4	■	■	–	–	16	0.327	cpv
CPV10-FB-6	■	■	–	–	16	0.465	cpv
CPV10-FB-8	■	■	–	–	16	0.604	cpv
CPV14-FB-4	■	■	–	–	16	0.419	cpv
CPV14-FB-6	■	■	–	–	16	0.603	cpv
CPV14-FB-8	■	■	–	–	16	0.788	cpv
CPV18-FB-4	■	–	–	–	16	0.624	cpv
CPV18-FB-6	■	–	–	–	16	0.911	cpv
CPV18-FB-8	■	–	–	–	16	1.197	cpv
MPA-S	–	■	■	–	32	3.25	mpa-s
CPV-SC	–	■	–	–	16	0.875	cpv-sc
CTEU-CP	–	■	–	0/16/32	0/16/32	3.4	54

## Selection aid

### Accessory selection aid

Connection M8, 3-pin



#### Note

Festo delivers pre-assembled M8/ M12 connecting cables (NEBU modular system) on request:

- Tailored to the application
- Perfectly fitting
- Easy to install


#### [1] Input modules

Type
CP-E16-M8
CP-E16-M8-Z
CP-E16-M8-EL

#### Plug/connecting cable

Type	Connection technology
<b>[2] Plugs</b>	
SEA-GS-M8	Solder lug
SEA-3GS-M8-S	Screw terminal
<b>[3] Connecting cable</b>	
NEBU-...-M8G3	M8 socket, 3-pin
	M8 socket, 4-pin
	M12 socket, 5-pin
	Open cable end

Connection for inputs M12, 5-pin



#### [1] Input modules

Type
CP-E16-M12x2-5POL
CP-E16N-M12-EL


#### [2] Plugs

Type	Connection technology
SEA-M12-5GS-PG7	Screw terminal
SEA-5GS-11-DUO	Screw terminal

## Selection aid

### Accessory selection aid

Connection for outputs M12, 5-pin



[1] Output modules		Plug/connecting cable	
Type		Type	Connection technology
CP-A08-M12-5POL		[2] Connecting cable	
CP-A08-M12-EL-Z		NEBU-...-M12G5	M12 socket, 5-pin
CP-A04-M12-CL		(modular system for a choice of connecting cables)	Open cable end
		[3] Plugs	
		SEA-M12-5GS-PG7	Screw terminal
		SEA-5GS-11-DUO	Screw terminal

## Datasheet – Input modules CP-E16

### Function

Digital input modules make it easier to connect proximity switches or other 24 V DC sensors (inductive, capacitive, etc.).

M12 plugs with double allocation are separated using a sensor/actuator distributor.

### Area of application

- Input modules for 24 V DC sensor signals
- M8 and M12 plugs, single allocation with 16 connections, double allocation with 8 connections
- M12 plug, 5-pin
- The input statuses for each input signal are indicated via an assigned LED.
- 24 V DC supply provided for all connected sensors
- Diagnostic LED for short circuit/undervoltage of sensor supply.
- Diagnostic LED for short circuit/interruption of external sensor supply with CP-E-16-M8-Z.



General technical data			CP-E16-M8	CP-E16-M12x2-5POL
Type			Positive switching	Positive switching
Number of inputs			16	
Allocation of inputs			Single allocation	Double allocation
Sensor connection type			16x M8, 3-pin	8x M12, 5-pin
Power supply 24 V DC			Coming from the bus node	
Intrinsic current consumption of electronics		[mA]	40	90
Input current at 24 V DC (from sensor)		[mA]	Typically 8	Typically 6
Fuse protection for sensors and electronics modules			Internal electronic short circuit protection	
Max. current consumption of sensor supply, aggregate current		[A]	Max. 0.5	
Sensor supply voltage		[V DC]	24 ±25%	
Reverse-polarity protection			For logic and sensor voltage	
Galvanic isolation			None	
Switching level				
	Signal 0	[V]	≤5	≤6
	Signal 1	[V]	≥11	≥8.6
Input delay		[ms]	Typically 5	Typically 3
Switching logic			PNP	PNP
Input characteristic			To IEC 1131-2	
Connection to bus node			Via pre-assembled cables	
Degree of protection to EN 60529			IP65 (when fully plugged in or fitted with protective cover)	
Temperature range				
	Operation	[°C]	-5 ... +50	
	Storage	[°C]	-20 ... +70	
Material			Die-cast aluminium	
PWIS conformity			VDMA24364-B2-L	
Dimensions		[mm]	148.9 x 66 x 47.9	140.9 x 78 x 55.2
Weight		[g]	400	500



## Datasheet – Input modules CP-E16

General technical data				
Type	CP-E16-M8-Z Positive and negative switching			
Number of inputs	16			
Allocation of inputs	Single allocation			
Sensor connection type	16x M8, 3-pin			
Power supply 24 V DC	Coming from the bus node, connection for additional sensor supply			
Intrinsic current consumption of electronics	[mA]	40		
Input current at 24 V DC (from sensor)	[mA]	Typically 8		
Fuse protection for sensors and electronics modules	Electronic short circuit protection per group			
Max. current consumption of sensor supply, aggregate current	[A]	Max. 1 per group of 8 inputs		
Sensor supply voltage	[V DC]	24 ±25%		
Reverse-polarity protection	For logic and sensor voltage			
Galvanic isolation	None			
Switching level		PNP	NPN	
	Signal 0	[V]	≤6	≥-8.6
	Signal 1	[V]	≥8.6	≤-6
Input delay	[ms]	Typically 3		
Switching logic	PNP/NPN			
Input characteristic	To IEC 1131-2			
Connection to bus node	Via pre-assembled cables			
Degree of protection to EN 60529	IP65 (when fully plugged in or fitted with protective cover)			
Temperature range	Operation	[°C]	-5 ... +50	
	Storage	[°C]	-20 ... +70	
Material	Die-cast aluminium			
PWIS conformity	VDMA24364-B2-L			
Dimensions	[mm]	216.9 x 66 x 50.6		
Weight	[g]	420		

Certifications			
Type	CP-E16-M...		
ATEX category for gas	II 3G		
Type of ignition protection for gas	Ex ec IICT5 GcX		
ATEX category for dust	II 3D		
Type of ignition protection for dust	Ex tc IIIC T80°C IP65 Dc X		
ATEX ambient temperature	[°C]	-5 ≤ Ta ≤ +50	
Explosion protection certification outside the EU	EPL Dc (GB)		
	EPL Gc (GB)		
CE marking (see declaration of conformity)	To EU EMC Directive <sup>1)</sup>		
	To EU Explosion Protection Directive (ATEX)		
	To EU RoHS Directive		
UKCA marking (see declaration of conformity)	To UK instructions for EMC		
	To UK EX instructions		
	To UK RoHS instructions		
KC mark	KC EMC		
Certification	c UL us - Recognized (OL)		
	RCM Mark		


1) For information about the area of use, see the EC declaration of conformity at: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/...) → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

## Datasheet – Input modules CP-E16

### Connection and display components

CP-E16-M12x2-5POL



- [1] CP connection
- [2] Slot for identification labels (IBS-6x10)
- [3] Identification of input type:  
-INPUT-P for PNP inputs
- [4] Status LED (green)
- [5] Sensor connections
- [6] Green LED for status indication (one LED per input)

### Pin allocation for sensor connections CP-E16-M12x2-5Pol


Pin allocation	Pin	Signal	Designation	Pin	Signal
	1	24 V	Operating voltage 24 V	1	24 V
	2	Ix+1*	Sensor signal	2	Ix+3*
	3	0 V	Operating voltage 0 V	3	0 V
	4	Ix*	Sensor signal	4	Ix+2*
	5	Ground	Earth terminal	5	Ground

\* Ix = Input x

## Datasheet – Input modules CP-E16

### Connection and display components

CP-E16-M8-Z



- [1] CP connection
- [2] Status LED (green)
- [3] Slot for identification labels (IBS-6x10)
- [4] Connection for the power supply to the external sensors
- [5] Red LED for indicating short circuit or failure of the sensor voltage (one LED per input group)
- [6] Sensor connections
- [7] Green LED for status indication (one LED per input)

#### Pin allocation for external sensor supply CP-E16-M8-Z

Pin allocation	Pin	Signal	Designation	
	1	24 V DC ±25%	Operating voltage	<p><b>Note</b></p> <p>External sensor supply for CP-E16-M8-Z: Specified for PNP or NPN operation (type CP-E16-M8-Z).</p> <p>The input module provides PNP or NPN inputs. You can determine either PNP or NPN operation by installing a bridge in the socket of the sensor supply connection.</p>
	2	PNP/NPN	Coding with negative/positive switching: <ul style="list-style-type: none"> <li>• PNP operation (pin 2 and 3 bridged)</li> <li>• NPN operation (pin 2 and 1 bridged)</li> </ul>	
	3	0 V	Operating voltage 0 V	
	4	n.c.	Not connected	
	5	Ground	Earth terminal	

#### Pin allocation – Sensor connections CP-E16-M8-Z


Pin allocation	Pin	Signal	Designation	Pin	Signal
	1	24 V	Operating voltage 24 V	1	24 V
	3	0 V	Operating voltage 0 V	3	0 V
	4	Ix*	Sensor signal	4	Ix+1*

\* Ix = Input x

## Datasheet – Input modules CP-E16

### Connection and display components

CP-E16-M8









- [1] CP connection
- [2] Slot for identification labels (IBS-6x10)
- [3] Status LED (green)
- [4] Sensor connections
- [5] Green LED for status indication (one LED per input)

### Pin allocation – Sensor connections CP-E16-M8

Pin allocation	Pin	Signal	Designation	Pin	Signal
	1	24 V	Operating voltage 24 V	1	24 V
	3	0 V	Operating voltage 0 V	3	0 V
	4	Ix*	Sensor signal	4	Ix+1*

\* Ix = Input x

## Accessories – Input modules CP-E16

Ordering data		Part no.	Type			
Designation						
<b>Input modules</b>						
	Positive switching	18205	CP-E16-M8			
	Positive switching	175561	CP-E16-M12x2-5POL			
	Positive and negative switching	189670	CP-E16-M8-Z			
<b>Power supply</b>						
	Power supply socket, straight, M12x1, 5-pin	18324	FBSD-GD-9-5POL			
<b>Sensor plug</b>						
	Plug, straight socket, M12x1	5-pin	PG7	175487	SEA-M12-5GS-PG7	
		4-pin	PG7	18666	SEA-GS-7	
		4-pin	2.5 mm <sup>2</sup> O.D.	192008	SEA-4GS-7-2.5	
	Plug, straight, M8x1	3-pin	Solderable	18696	SEA-GS-M8	
	Plug for 2 connecting cables, M12x1, PG11	4-pin	Screw-in	192009	SEA-3GS-M8-S	
				18779	SEA-GS-11-DUO	
		5-pin	192010	SEA-5GS-11-DUO		
<b>Connecting cables</b>						
	Connecting cable M8-M8	3-pin	Straight plug/ straight socket	0.5 m	541346	NEBU-M8G3-K-0.5-M8G3
				1.0 m	541347	NEBU-M8G3-K-1-M8G3
				2.5 m	541348	NEBU-M8G3-K-2.5-M8G3
				5.0 m	541349	NEBU-M8G3-K-5-M8G3
	Modular system for a choice of connecting cables				–	NEBU-...
<b>Mounting</b>						
	Mounting for H-rail	170169	CP-TS-HS35			

## Datasheet – Input modules CP-E...-EL


### Function

Digital input modules make it easier to connect proximity switches or other 24 V DC sensors (inductive, capacitive, etc.).

Plugs with double allocation are separated using a sensor/actuator distributor.

### Area of application

- Input modules for 24 V DC sensor signals
- M8 and M12 connection technology
- Display of the input statuses for each input signal via an assigned LED
- Operating voltage supply 24 V DC for all connected sensors
- Diagnostic LED for short circuit/overload of sensor supply
- Circumferential labelling with large, hinged inscription label
- Earthing plate and H-rail mounting already integrated



General technical data		CP-E16-M12-EL	CP-E16-M8-EL
Type		Positive switching	Positive switching
Number of inputs		16	
Allocation of inputs		Double allocation	Single allocation
Sensor connection type		8x M12, 5-pin	16x M8, 3-pin
Power supply 24 V DC		Via CP connection	
Intrinsic current consumption at operating voltage	[mA]	Typically 75	
Fuse protection (short circuit)		Internal electronic fuse protection for each group	
Max. aggregate current per module	[A]	0.7	
Nominal operating voltage		24	
Operating voltage range	[V DC]	18 ... 30	
Residual ripple load voltage	[Vss]	4	
Electrical isolation between channels		None	
Switching level	Signal 0	[V]	≤ 6
	Signal 1	[V]	≥ 8.6
Debounce time at inputs	[ms]	3 (0.5 ms, 10 ms, 20 ms parameterisable)	
Switching logic		PNP	
Input characteristic		To IEC 1131-T2	
Connection to bus node		Via pre-assembled cables	
Diagnostics		CP communication	
		Short circuit/overload	
		Undervoltage	
LED displays		2 module diagnostics	2 module diagnostics
		16 channel status	16 channel status
		4 group diagnostics	4 group diagnostics

## Datasheet – Input modules CP-E...-EL

Materials	
Housing	Reinforced PA
Cover	Reinforced PA
Note on materials	RoHS-compliant
PWIS conformity	VDMA24364-B2-L
Operating and environmental conditions	
Degree of protection to EN 60529	IP65/IP67 (when fully plugged in or fitted with protective cap)
Ambient temperature [°C]	-5 ... +50
Storage temperature [°C]	-20 ... +70
Corrosion resistance class CRC <sup>1)</sup>	1
CE marking (see declaration of conformity)	To EU EMC Directive <sup>2)</sup> To EU RoHS Directive <sup>2)</sup>
UKCA marking (see declaration of conformity)	To UK instructions for EMC <sup>2)</sup> To UK RoHS instructions <sup>2)</sup>
KC mark	KC EMC
Certification	c UL us listed (OL) RCM mark C-Tick

1) More information: [www.festo.com/x/topic/kbk](http://www.festo.com/x/topic/kbk)


2) For information about the area of use, see the EC declaration of conformity at: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/...) → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

## Datasheet – Input modules CP-E...-EL

### Connection and display components


CP-E16-M12-EL



- [1] CP connection, outgoing
- [2] CP connection, incoming
- [3] Status LED (module) for short circuit/overload of sensor supply (red)
- [4] Status LED for CP communication (green)
- [5] Status LEDs for inputs (status indication, green)
- [6] Status LED (group) for short circuit/overload of sensor supply (red)
- [7] Fixture for inscription label holder ASCF-H-E2
- [8] Sensor connections (2 inputs per socket)

### Pin allocation for sensor connections CP-E16-M12-EL

Pin allocation



Pin	Signal	Designation
1	24 V	Operating voltage 24 V
2	Ix+1*	Sensor signal
3	0 V	Operating voltage 0 V
4	Ix*	Sensor signal
5	Ground	Earth terminal


\* Ix = Input x



## Datasheet – Input modules CP-E...-EL

### Connection and display components

CP-E16-M8-EL



- [1] CP connection, outgoing
- [2] CP connection, incoming
- [3] Status LED (module) for short circuit/overload of sensor supply (red)
- [4] Status LED for CP communication (green)
- [5] Status LEDs for inputs (status indication, green)
- [6] Status LED (group) for short circuit/overload of sensor supply (red)
- [7] Fixture for inscription label holder ASCF-H-E2
- [8] Sensor connections (1 input per socket)








### Pin allocation for sensor connections CP-E16-M8-EL

Pin allocation

Pin allocation	Pin	Signal	Designation
	1	24 V	Operating voltage 24 V
	3	0 V	Operating voltage 0 V
	4	Ix*	Sensor signal

\* Ix = Input x

## Accessories – Input modules CP-E...-EL

Ordering data				Part no.	Type	
Designation						
<b>Input modules</b>						
	Positive switching			546923	CP-E16-M12-EL	
	Positive switching			546922	CP-E16-M8-EL	
<b>Plug</b>						
	Plug, straight socket, M12x1	5-pin	PG7	175487	SEA-M12-5GS-PG7	
		4-pin	PG7	18666	SEA-GS-7	
	Plug, straight, M8x1	4-pin	2.5 mm <sup>2</sup> O.D.	192008	SEA-4GS-7-2.5	
		3-pin	Solderable	18696	SEA-GS-M8	
	Plug for 2 connecting cables, M12x1, PG11		Screw-in	192009	SEA-3GS-M8-S	
		4-pin		18779	SEA-GS-11-DUO	
		5-pin		192010	SEA-5GS-11-DUO	
<b>Distributors</b>						
	Modular system for all types of sensor/actuator distributor			-	NEDY... → Internet: nedy	
	Push-in T-connector	1x plug M8, 4-pin	2x socket M8, 3-pin	8005312	NEDY-L2R1-V1-M8G3-N-M8G4	
		1x plug M12, 4-pin	2x socket M8, 3-pin	8005311	NEDY-L2R1-V1-M8G3-N-M12G4	
			2x socket M12, 5-pin	8005310	NEDY-L2R1-V1-M12G5-N-M12G4	
<b>Inscription label holders</b>						
	Inscription label holders for EL modules, bag of 10			547473	ASCF-H-E2	
<b>User documentation</b>						
	User documentation for input/output modules			German	539299	P.BE.-CPEA-CL-DE
				English	539300	P.BE.-CPEA-CL-EN
				French	539302	P.BE.-CPEA-CL-FR
				Italian	539303	P.BE.-CPEA-CL-IT
				Spanish	539301	P.BE.-CPEA-CL-ES


## Datasheet – Output modules CP-A08

### Function

The electrical outputs control actuators such as individual valves, lamps, signal equipment and much more.

### Area of application

- Output module with 8 outputs  
24 V DC
- M12 connection technology, 5-pin socket
- LED display of the switching status per channel
- Short circuit and overload detection
- Malfunction display by a green LED



### Note

Optimum actuation of valves with M12 central plug.

### General technical data

Type	CP-A08-M12-5POL Positive switching	
Number of outputs	8	
Allocation of outputs	Single allocation	
Output connection type	8x M12, 5-pin	
Load voltage connection	M18, 4-pin	
Bus connection	2 plugs M9, 5-pin, via prefabricated cables	
Max. output current per channel	[A]	0.5
Operating voltage	[V DC]	24 ±25%
Load voltage connection	[V DC]	24 ±25%, reverse polarity protected
Fuse protection for power output	[A]	Electronic fuse per output 0.5
Intrinsic current consumption of electronics	[mA]	Max. 90
Overload/short circuit protection	Per channel	
Switching logic	PNP to IEC 1131-2	
Degree of protection to EN 60529	IP65 (when fully plugged in or fitted with protective cover)	
Temperature range	Operation	[°C] -5 ... +50
	Storage	[°C] -20 ... +70
Material	Die-cast aluminium	
PWIS conformity	VDMA24364-B2-L	
Dimensions (LxWxD)	[mm]	172.9 x 78 x 57.1
Weight	[g]	500

### Certifications

ATEX category for gas	II 3G
Type of ignition protection for gas	Ex ec IICT5 Gc X
ATEX category for dust	II 3D
Type of ignition protection for dust	Ex tc IIIC T80°C IP65 Dc X
ATEX ambient temperature	[°C] -5 ≤ Ta ≤ +50
Explosion protection certification outside the EU	EPL Dc (GB) EPL Gc (GB)
CE marking (see declaration of conformity)	To EU EMC Directive <sup>1)</sup>
	To EU Explosion Protection Directive (ATEX)
	To EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK instructions for EMC
	To UK EX instructions
	To UK RoHS instructions
KC mark	KC EMC
Certification	c UL us - Recognized (OL)


1) For information about the area of use, see the EC declaration of conformity at: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/...) → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

## Datasheet – Output modules CP-A08

### Connection and display components

CP-A08-M12...



- [1] Load voltage connection
- [2] CP connection, incoming
- [3] Slot for identification labels (IBS-6x10)
- [4] Identification for output type:
  - OUTPUT-P for PNP outputs
  - OUTPUT-N for NPN outputs
- [5] Status LED (green)
- [6] CP connection, outgoing
- [7] Connections for actuators
- [8] Yellow LED for status display (one LED per input)

#### Pin allocation for load voltage connection CP-A08-M12...

Pin allocation	Pin	Signal	Designation
	1	n.c.	Not connected
	2	24 V DC ±25%	Operating voltage
	3	0 V	Operating voltage 0 V
	4	FE	Protective earthing

#### Pin allocation for outputs









Pin allocation	Pin	Signal	Designation	Pin	Signal
<b>CP-A08-M12-5POL (PNP outputs)</b>					
	1	n.c.	Not connected	1	n.c.
	2	Ox+1	Connected with pin 4 of plug 2/not connected	2	n.c.
	3	0 V	Reference potential	3	0 V
	4	Ox	Output/connected with pin 2 of plug 1	4	Ox+1
	5	Ground	Earth terminal	5	Ground

**Note**

Two outputs can be connected to connections 0, 2, 4 and 6 of the CP output module via an internal connection between pin 2 of the even numbered output and pin 4 of the opposite odd numbered output.

\* Ox = Output x


## Accessories – Output modules CP-A08

Ordering data		Part no.	Type
Designation			
<b>Output modules</b>			
	Positive switching	175640	CP-A08-M12-5POL
<b>Power supply</b>			
	Power supply socket, straight, M18x1, 4-pin	For 1.5 mm <sup>2</sup>	18493 NTSD-GD-9
		For 2.5 mm <sup>2</sup>	18526 NTSD-GD-13.5
	Power supply socket, angled, M18x1, 4-pin	For 1.5 mm <sup>2</sup>	18527 NTSD-WD-9
		For 2.5 mm <sup>2</sup>	533119 NTSD-WD-11
<b>Sensor plug</b>			
	Plug, straight socket, M12x1	5-pin	175487 SEA-M12-5GS-PG7
	Plug for 2 connecting cables, M12x1, PG11	4-pin	18779 SEA-GS-11-DUO
		5-pin	192010 SEA-5GS-11-DUO
<b>Distributors</b>			
	Modular system for all types of sensor/actuator distributor	–	NEDY-... → Internet: nedy
<b>Connecting cable</b>			
	Modular system for a choice of connecting cables	–	NEBU-... → Internet: nebu
<b>Mounting</b>			
	Mounting for H-rail	170169	CP-TS-HS35

## Datasheet – Output modules CP-A08-EL

### Function

The electrical outputs control actuators such as individual valves, lamps, signal equipment and much more.




### Note

The output module is ideal for actuation of valves with M12 central plug.

### Area of application

- Output module with 8 outputs 24 V DC
- M12, 5-pin connection technology
- Display of the switching status per channel via LED
- Short circuit and overload detection
- Malfunction display by a red LED
- Module supports the CPI functionality (only in combination with the CPX CP interface)
- Circumferential labelling with large, hinged inscription label
- Earthing plate and H-rail mounting already integrated



General technical data		
Type		CP-A08-M12-EL-Z Positive switching
Number of outputs		8
Allocation of outputs		Connection 1, 3, 5 and 7 with double allocation, connection 2, 4, 6 and 8 with single allocation
Sensor connection type		8x M12, 5-pin
Power supply 24 V DC		M12, 4-pin, A-coded
Intrinsic current consumption at operating voltage	[mA]	Typically 35
Max. aggregate current per module	[A]	4
Max. output current per channel	[A]	Max. 0.5, max. 2 outputs can be connected in parallel
Nominal operating voltage	[V DC]	24
Operating voltage range	[V DC]	18 ... 30
Residual ripple load voltage	[Vss]	4
Note concerning load voltage		Via load voltage connection (24 V DC)
Fuse protection (short circuit)		Internal electronic fuse protection for each group
Switching logic		PNP
Output characteristic		To ICE 1131-T2
Electrical isolation between channels		None
Connection to bus node		Via pre-assembled cables
Diagnostics		CP communication Short circuit/overload per channel Undervoltage
LED displays		3 module diagnostics 8 channel status 8 channel diagnostics

Materials		
Housing		Reinforced PA
Cover		Reinforced PA
Note on materials		RoHS-compliant
PWIS conformity		VDMA24364-B2-L

## Datasheet – Output modules CP-A08-EL

Operating and environmental conditions	
Degree of protection to EN 60529	IP65/IP67 (when fully plugged in or fitted with protective cap)
Ambient temperature	[°C] -5 ... +50
Storage temperature	[°C] -20 ... +70
Corrosion resistance class CRC <sup>1)</sup>	1
CE marking (see declaration of conformity)	To EU EMC Directive <sup>2)</sup> To EU RoHS Directive <sup>2)</sup>
UKCA marking (see declaration of conformity)	To UK instructions for EMC <sup>2)</sup> To UK RoHS instructions <sup>2)</sup>
KC mark	KC EMC
Certification	c UL us listed (OL) RCM mark C-Tick


1) More information: [www.festo.com/x/topic/kbk](http://www.festo.com/x/topic/kbk)

2) For information about the area of use, see the EC declaration of conformity at: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/...) → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

### Connection and display components


CP-A08-M12-EL-Z



- [1] CP connection, outgoing
- [2] CP connection, incoming
- [3] Status LED (module) for short circuit/overload of sensor supply (red)
- [4] Status LED for CP communication (green)
- [5] Status LED for load supply (PL, green)
- [6] Status LEDs for outputs (status display, yellow)
- [7] Status LED for output (channel) short circuit/overload (red)
- [8] Fixture for inscription label holder ASCF-H-E2
- [9] 8 outputs (1 output per socket)

### Pin allocation for load voltage connection CP-A08-M12-EL-Z

Pin allocation



Pin	Signal	Designation
1	n.c.	Not connected
2	24 V DC ±25%	Operating voltage
3	0 V	Operating voltage 0 V
4	FE	Protective earthing


## Datasheet – Output modules CP-A08-EL

**Pin allocation for outputs**

Pin allocation

Output 1, 3, 5 and 7		Designation
Pin	Signal	

**CP-A08-M12-EL-Z (odd number of PNP outputs)**



1	n.c.	Not connected
2	Ox+1	Connected with pin 4 of output 2
3	0 V	Reference potential
4	Ox	Output
5	FE	Earth terminal

**Note**  
Two outputs can be connected to each of connections 1, 3, 5 and 7 of the CP output module via an internal connection between pin 2 of the odd numbered output and pin 4 of the underlying even numbered output.


\* Ox = Output x

**Pin allocation for outputs**

Pin allocation

Output 2, 4, 6 and 8		Designation
Pin	Signal	

**CP-A08-M12-EL-Z (even number of PNP outputs)**









1	n.c.	Not connected
2	n.c.	Not connected
3	0 V	Reference potential
4	Ox+1	Connected with pin 2 of output 1
5	FE	Earth terminal


\* Ox = Output x





## Accessories – Output modules CP-A08-EL

Ordering data		Part no.	Type
Designation			
<b>Output module</b>			
	Positive switching	546924	CP-A08-M12-EL-Z
<b>Plug</b>			
	Plug, straight socket, M12x1	5-pin	PG7
		4-pin	PG7
		4-pin	2.5 mm <sup>2</sup> O.D.
	Plug for 2 connecting cables, M12x1, PG11	4-pin	18779
		5-pin	192010
<b>Distributors</b>			
	Modular system for all types of sensor/actuator distributor	–	NEDY-... → Internet: nedy
<b>Inscription label holders</b>			
	Inscription label holders for EL modules, bag of 10	547473	ASCF-H-E2
<b>User documentation</b>			
	User documentation for input/output modules	German	539299
		English	539300
		French	539302
		Italian	539303
		Spanish	539301
			P.BE.-CPEA-CL-DE
			P.BE.-CPEA-CL-EN
			P.BE.-CPEA-CL-FR
			P.BE.-CPEA-CL-IT
			P.BE.-CPEA-CL-ES


## Datasheet – Valve terminals MPA-S


-  Flow rate  
MPA1: up to 360 l/min  
MPA14: up to 550 l/min  
MPA2: up to 700 l/min

-  Valve width  
MPA1: 10 mm  
MPA14: 14 mm  
MPA2: 21 mm

-  Voltage  
24 V DC

CPI interface for communication between a valve terminal MPA-S and a CPI master. It activates a valve terminal MPA-S with up to 32 solenoid coils on max. 16 valve positions. It is also possible to install an additional electrical supply at any other point on the valve terminal to create different voltage zones.



-  **Note**

An additional electrical supply is essential for more than 16 MPA2 solenoid coils (more than 4 electronics modules).

Please note that without an additional electrical supply a maximum of 24 solenoid coils can be connected at the same time.

If more than 24 MPA1, 24 MPA14 or 12 MPA2 solenoid coils are to be connected at the same time, an additional supply must be connected at the latest after the third electronics module.

General technical data			MPA-CPI-VI
Type			
CP interface, incoming			Plug M9, 5-pin
CP interface, outgoing			M9 socket, 5-pin
Max. no. of valve positions			32
Max. number of pressure zones			9
LED display (product-specific)	PS		Common message regarding power supply
	PL		Power supply for valves
	Symbol		Module error
Nominal operating voltage		[V DC]	24
Permissible voltage fluctuations		[V DC]	±25%
Power failure buffering	Logic side only	[ms]	10
Current consumption at nominal operating voltage	Load	[mA]	Dependent on valve type and number of valves
	Electronics	[mA]	Approx. 50 (plus current consumption of electronics modules)
Residual ripple		[Vss]	4
Materials			Die-cast aluminium, PA
Note on materials			RoHS-compliant
PWIS conformity			VDMA24364-B1/B2-L
Dimensions			→ Internet: mpa-s
Weight		[g]	220
Technical data on valves			→ Internet: mpa-s
Degree of protection			IP67

## Datasheet – Valve terminals MPA-S


Operating and environmental conditions	
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Operating pressure	[MPa] -0.09 ... +1
	[bar] -0.9 ... +10
Pilot pressure	[MPa] 0.3 ... 0.8
	[bar] 3 ... 8
Ambient temperature	[°C] -5 ... +50
Temperature of medium	[°C] -5 ... +50
Storage temperature	[°C] -20 ... +40
Relative humidity	Max. 90% at 40°C
CE marking (see declaration of conformity)	To EU EMC Directive <sup>1)</sup>
	To EU RoHS Directive
	To EU Explosion Protection Directive (ATEX)
UKCA marking (see declaration of conformity)	To UK instructions for EMC
	To UK RoHS instructions
	To UK EX instructions
KC mark	KC EMC
Certification	c UL us - Recognized (OL)
	RCM

1) For information about the area of use, see the EC declaration of conformity at: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/...) → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.




ATEX	
ATEX category for gas	II 3G
Type of ignition protection for gas	Ex ec IIC T4 Gc X
Explosion-proof ambient temperature	[°C] -5 ≤ Ta ≤ +50
Explosion protection certification outside the EU	EPL Dc (GB)
	EPL Gc (GB)

## Connection and display components





- [1] CP connection, incoming
- [2] CP connection, outgoing
- [3] Status LEDs
  - CP system supply (green)
  - Load supply (green)
  - Module fault (red)

## Datasheet – Valve terminals MPA-S

Ordering data				
Designation		Part no.	Type	
<b>Valve terminal MPA-S</b>				
	With CPI interface	546280	MPA-CPI-VI	
<b>Valve terminal connection</b>				
	Connecting cable WS-WD	0.25 m	540327	KVI-CP-3-WS-WD-0.25
		0.5 m	540328	KVI-CP-3-WS-WD-0.5
		2 m	540329	KVI-CP-3-WS-WD-2
		5 m	540330	KVI-CP-3-WS-WD-5
	Connecting cable GS-GD	8 m	540331	KVI-CP-3-WS-WD-8
		2 m	540332	KVI-CP-3-GS-GD-2
		5 m	540333	KVI-CP-3-GS-GD-5
		8 m	540334	KVI-CP-3-GS-GD-8


## Datasheet – CPV-SC valve terminals

-  - Flow rate  
170 l/min

-  - Valve width  
10 mm

-  - Voltage  
24 V DC

CPI interface for communication between a CPV-SC valve terminal and a CPI master. It activates a valve terminal CPV-SC with up to 16 solenoid coils.



General technical data			CPVSC1-AE16-CPI
Type			CPVSC1-AE16-CPI
Types of communication			CP fieldbus
Log			CP fieldbus
Fieldbus interface			M9, 5-pin, plug and socket
Max. no. of solenoid coils			16
LED display (bus-specific)			CP: CP fieldbus
Device-specific diagnostics			Undervoltage of valve terminal
Parameterisation			Parameterisation via CP protocol
Reverse-polarity protection			For all electrical operating voltage connections
Current consumption at nominal operating voltage	Electronics	[mA]	≤100
	Load		Dependent on valve type and number of valves
Protection against direct and indirect contact			PELV
Housing material			Reinforced PA
Note on materials			RoHS-compliant
PWIS conformity			VDMA24364-B2-L
Type of mounting			Via through-hole
Width	[mm]		52
Height	[mm]		40
Length	[mm]		70
Product weight	[g]		150
Technical data on valves			→ Internet: cpv-sc
Degree of protection			IP20
			To IEC 60529

## Datasheet – CPV-SC valve terminals


Operating and environmental conditions		
Ambient temperature	[°C]	-5 ... +50
Storage temperature	[°C]	-20 ... +50
Relative humidity		90% at 50°C
		Non-condensing
Corrosion resistance class CRC <sup>1)</sup>		1
CE marking (see declaration of conformity)		To EU EMC Directive <sup>2)</sup>
Certification		cUL us - Recognized (OL)

1) More information: [www.festo.com/x/topic/kbk](http://www.festo.com/x/topic/kbk)

2) For information about the area of use, see the EC declaration of conformity at: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/...) → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

### Connection and display components



- [1] CP connection, incoming
- [2] CP connection, outgoing
- [3] Status LED for CP communication
- [4] Status LEDs for valves


### Ordering data

Designation	Part no.	Type
-------------	----------	------




#### Valve terminal CPV-SC

	With CPI interface	541975	CPVSC1-AE16-CPI
--	--------------------	--------	-----------------

#### Valve terminal connection

	Connecting cable WS-WD	0.25 m	540327	KVI-CP-3-WS-WD-0.25
		0.5 m	540328	KVI-CP-3-WS-WD-0.5
		2 m	540329	KVI-CP-3-WS-WD-2
		5 m	540330	KVI-CP-3-WS-WD-5
		8 m	540331	KVI-CP-3-WS-WD-8
	Connecting cable GS-GD	2 m	540332	KVI-CP-3-GS-GD-2
		5 m	540333	KVI-CP-3-GS-GD-5
		8 m	540334	KVI-CP-3-GS-GD-8


## Datasheet – Bus node CTEU

-  - Flow rate  
Dependent on the connected valve terminal
-  - Valve width  
Dependent on the connected valve terminal
-  - Voltage  
24 V DC

CPI interface for communication between a valve terminal or input modules with I-Port interface and a CPI master.

Valve terminals with I-Port interface

- CPV
- MPA-L
- VTUG



General technical data			
Type	CTEU-CP		
Log	CPI-B		
Diagnostics	Communication error		
	System diagnostics		
	Undervoltage		
Parameterisation	Diagnostic behaviour		
	Fail-safe response		
Configuration support	None		
Control elements	DIL switch		
LED display	Product-specific	PS: Operating voltage for electronics and load supply	
	Bus-specific	X1: System status of module at I-Port 1	
X2: System status of module at I-Port 2			
Maximum address capacity	Inputs	[byte]	4
	Outputs	[byte]	4
Type of mounting	On electrical interface		
	On electrical connection block		
Degree of protection	IP65		
	IP67		
Note on degree of protection	In assembled state		
	Unused connections sealed		
Dimensions W x L x H	[mm]	40 x 91 x 50	
Grid dimension	[mm]	40	
Product weight	[g]	105	

Technical data Fieldbus interface			
Fieldbus interface			
Log	CPI-B		
Function	Incoming bus connection		
	Power supply		
Transmission rate	[kbps]	1000	
Type	CP installation system		
Connection type	Plug		
Connection technology	M9x0.5		
Number of pins/wires	5		
Internal cycle time	2 ms per 2 bytes of user data		
Fieldbus interface 2			
Function	Bus connection outgoing		
	Power supply		
Connection type	Socket		
Connection technology	M9x0.5		
Number of pins/wires	5		

## Datasheet – Bus node CTEU

Technical data – Electrics		
Nominal operating voltage	[V DC]	24
Operating voltage range	[V DC]	18 ... 30
Intrinsic current consumption at nominal operating voltage	[mA]	Typically 50
Max. power supply	[A]	3.4
Power failure buffering	[ms]	10
Operating and environmental conditions		
Ambient temperature	[°C]	-5 ... +50
Storage temperature	[°C]	-20 ... +70
Corrosion resistance class CRC <sup>1)</sup>		2
CE marking (see declaration of conformity)		To EU EMC Directive <sup>2)</sup> To EU RoHS Directive
UKCA marking (see declaration of conformity)		To UK instructions for EMC To UK RoHS instructions
KC mark		KC EMC
Certification		c UL us - Listed (OL) RCM


1) More information: [www.festo.com/x/topic/kbk](http://www.festo.com/x/topic/kbk)

2) For information about the area of use, see the EC declaration of conformity at: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/...) → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Materials	
Housing	PA
Note on materials	RoHS-compliant
PWIS conformity	VDMA24364 zone III




### Connection and display components



- [1] CP connection, incoming
- [2] CP connection, outgoing
- [3] Status LED for CP communication
- [4] DIL switch



## Datasheet – Bus node CTEU


Ordering data		Part no.	Type
Designation			
<b>Bus node</b>			
	For valve terminals with I-Port interface	2149714	CTEU-CP
<b>Valve terminal connection</b>			
	Connecting cable WS-WD	0.25 m	540327 KVI-CP-3-WS-WD-0.25
		0.5 m	540328 KVI-CP-3-WS-WD-0.5
		2 m	540329 KVI-CP-3-WS-WD-2
		5 m	540330 KVI-CP-3-WS-WD-5
		8 m	540331 KVI-CP-3-WS-WD-8
	Connecting cable GS-GD	2 m	540332 KVI-CP-3-GS-GD-2
		5 m	540333 KVI-CP-3-GS-GD-5
		8 m	540334 KVI-CP-3-GS-GD-8

## Technical data

### Dimensions – Bus node

Download CAD data → [www.festo.com](http://www.festo.com)

CPX-FB... and CPX-CP-4-FB



[1] Mounting holes  
[2] Earthing screw

[3] H-rail  
[4] H-rail mounting

[5] CPX bus node


[6] CPX-CP interface

## Technical data

### Dimensions – Sturdy input modules

Download CAD data → [www.festo.com](http://www.festo.com)

CP-E16-M8




[1] Slots for inscription labels

[2] Earthing screw M3

[3] Protective caps (included in the scope of delivery)

[4] H-rail with support base

CP-E16-M8-Z



[1] Slots for inscription labels

[2] Earthing screw M3

[3] Protective caps (included in the scope of delivery)


[4] H-rail with support base

## Technical data

### Dimensions – Sturdy input modules

Download CAD data → [www.festo.com](http://www.festo.com)

CP-E16-M12x2-5POL



[1] Slots for inscription labels

[2] Earthing screw M3

[3] Protective caps (included in the scope of delivery)


[4] H-rail with support base

## Technical data

### Dimensions – Economical input modules


Download CAD data → [www.festo.com](http://www.festo.com)

CP-E16-M8-EL



- [1] Through-hole for surface mounting
- [2] H-rail
- [3] Mounting kit for H-rail (included in the scope of delivery)

CP-E16-M12-EL




- [1] Through-hole for surface mounting
- [2] H-rail
- [3] Mounting kit for H-rail (included in the scope of delivery)

Technical data

Dimensions – Economical input modules

Download CAD data → [www.festo.com](http://www.festo.com)

CP-A08-M12-5POL




- [1] Slots for inscription labels
- [2] Earthing screw M3
- [3] Protective caps (included in the scope of delivery)
- [4] H-rail with support base

Dimensions – Economical output module

Download CAD data → [www.festo.com](http://www.festo.com)

CP-A08-M12-EL-Z



- [1] Through-hole for surface mounting
- [2] H-rail
- [3] Mounting kit for H-rail (included in the scope of delivery)

## Order processing information

### Configuration guidelines

The CPI system supports a certain number of modules per CP string depending on the type of the CP master and the

CP modules connected.

CP masters and CP modules can be split into two different groups:

- With CPI functionality
- Without CPI functionality.

#### CP modules with CPI functionality

CP modules with CPI functionality offer the following features:

- Incoming and outgoing CP interface
- Any arrangement of the modules within a CP string

- Max. 4 modules per CP string
- Max. 32 inputs and 32 outputs can be connected to each string depending on the version

#### CP modules without CPI functionality

Sturdy CP modules offer the following features:

- CP valve terminals and CP output modules have an incoming and outgoing CP interface

- CP input modules only have an incoming CP interface and therefore can only be positioned at the end of a CP string
- All CP modules with CPI functionality can also be connected to CP masters without extended functionality.

### Information on using CP modules with and without CPI functionality

A mixture of CP modules with and without CPI functionality is possible. The following must be noted in this case:

- Only one input module without CPI functionality is possible per CP string (at the end of a CP string)

- Only one CP valve terminal or output module without CPI functionality is possible per CP string (any point in the CP string)

- Free positions in the CP string can be filled by CP modules with CPI functionality (max. 4 modules).

#### Note








The cable length for any given string may not exceed 10 m.

Connecting cables are available with lengths of 0.25 m, 0.5 m, 2 m, 5 m and 8 m

→ p. 56






No more than 32 inputs and 32 outputs (sum of all 4 CP modules on a CP string) may be connected, regardless of the type of CP module (with or without CPI functionality).

## Accessories

Ordering data				Part no.	Type	
Designation						
<b>Sensor plug</b>						
	Plug M8, 3-pin	Solderable	For NEDY-L2R1-V1-M8G3-N-M8G4	18696	SEA-GS-M8	
		Screw-in	For NEDY-L2R1-V1-M8G3-N-M8G4	192009	SEA-3GS-M8-S	
	Plug M12, 4-pin	Screw terminal	For cable $\varnothing$ 2.5 ... 2.9 mm	192008	SEA-4GS-7-2.5	
			For 2x cable $\varnothing$ 3 ... 5 mm	18779	SEA-GS-11-DUO	
			For cable $\varnothing$ 4 ... 6 mm	18666	SEA-GS-7	
	Plug, M12, 5-pin	Screw terminal	For 2x cable $\varnothing$ 2.5 ... 5 mm	192010	SEA-5GS-11-DUO	
For cable $\varnothing$ 4 ... 6 mm			175487	SEA-M12-5GS-PG7		
<b>Distributors</b>						
	Modular system for all types of sensor/actuator distributor			–	NEDY-... → Internet: nedy	
	Push-in T-connector	1x plug M8, 4-pin	2x socket M8, 3-pin	8005312	NEDY-L2R1-V1-M8G3-N-M8G4	
		1x plug M12, 4-pin	2x socket M8, 3-pin	8005311	NEDY-L2R1-V1-M8G3-N-M12G4	
			2x socket M12, 5-pin	8005310	NEDY-L2R1-V1-M12G5-N-M12G4	
<b>Connecting cable</b>						
	Connecting cable M8-M8	3-pin	Straight plug/straight socket	0.5 m	541346	NEBU-M8G3-K-0.5-M8G3
				1.0 m	541347	NEBU-M8G3-K-1-M8G3
				2.5 m	541348	NEBU-M8G3-K-2.5-M8G3
				5.0 m	541349	NEBU-M8G3-K-5-M8G3
	Connecting cable M12-M12	5-pin	Straight plug/straight socket	1.5 m	529044	KV-M12-M12-1.5
				3.5 m	530901	KV-M12-M12-3.5
Modular system for a choice of connecting cables				–	NEBU-... → Internet: nebu	
<b>Connecting cable – CP modules</b>						
	Angled plug/angled socket			0.25 m	540327	KVI-CP-3-WS-WD-0.25
				0.5 m	540328	KVI-CP-3-WS-WD-0.5
				2 m	540329	KVI-CP-3-WS-WD-2
				5 m	540330	KVI-CP-3-WS-WD-5
				8 m	540331	KVI-CP-3-WS-WD-8
	Straight plug/straight socket			2 m	540332	KVI-CP-3-GS-GD-2
				5 m	540333	KVI-CP-3-GS-GD-5
				8 m	540334	KVI-CP-3-GS-GD-8
	Connecting plug for CP cable (cabinet through-feed)			543252	KVI-CP-3-SSD	



## Accessories

Ordering data		Part no.	Type
Designation			
<b>Protective caps</b>			
	Cover cap for closing off unused connections (10 pieces)	For M8 connections	<b>177672</b> <b>ISK-M8</b>
		For M12 connections	<b>165592</b> <b>ISK-M12</b>
<b>Mounting components</b>			
	Mounting for H-rail, CP modules	<b>170169</b>	<b>CP-TS-HS35</b>
<b>Inscription labels</b>			
	Inscription labels 6x10 mm, in frame (64 pieces)	<b>18576</b>	<b>IBS-6x10</b>
	Inscription label holders for EL modules, bag of 10	<b>547473</b>	<b>ASCF-H-E2</b>
<b>Documentation</b>			
	User documentation for CPX-CP interface	German	<b>539293</b> <b>P.BE-CPX-CP-EN</b>
		English	<b>539294</b> <b>P.BE-CPX-CP-EN</b>
		Spanish	<b>539295</b> <b>P.BE-CPX-CP-ES</b>
		French	<b>539296</b> <b>P.BE-CPX-CP-FR</b>
		Italian	<b>539297</b> <b>P.BE-CPX-CP-IT</b>
	User documentation for compact input/output modules	German	<b>539299</b> <b>P.BE.-CPEA-CL-DE</b>
		English	<b>539300</b> <b>P.BE.-CPEA-CL-EN</b>
		French	<b>539302</b> <b>P.BE.-CPEA-CL-FR</b>
		Italian	<b>539303</b> <b>P.BE.-CPEA-CL-IT</b>
		Spanish	<b>539301</b> <b>P.BE.-CPEA-CL-ES</b>
	System description	German	<b>165126</b> <b>P.BE-CPSYS-DE</b>
		English	<b>165226</b> <b>P.BE-CPSYS-EN</b>
		French	<b>165128</b> <b>P.BE-CPSYS-FR</b>
		Italian	<b>165158</b> <b>P.BE-CPSYS-IT</b>
Spanish		<b>165228</b> <b>P.BE-CPSYS-ES</b>	