

## Valve terminals type 80 CPV-SC, Smart Cubic


**FESTO**



# Valve terminals type 80 CPV-SC, Smart Cubic

Key features

FESTO



## Innovative

- Small, compact valve terminal for a wide range of pneumatic applications
- Enormous flexibility during planning, assembly and operational use
- Multi-pin plug connection and fieldbus interface
- Wide range of selectable valve functions; 5/2-way, 3/2-way and 2/2-way functions
- With flow rates of up to 170 l/min, CPV-SC offers outstanding pneumatic performance for a wide range of applications
- Low weight

## Versatile

- Provides 2 ... 16 valve positions on one terminal
- Ideally suited for operating small pneumatic drives in tight spaces
- The flexibility of the pneumatic working ports provides a practical solution to different requirements
- Round silencers, integrated flat plate silencers or screw/plug connection for ducted exhaust air
- Suitable for vacuum
- Enables multiple pressure zones on a single valve terminal

## Reliable

- Manual override
- Durable thanks to the use of tried and tested piston spool valves
- Sturdy thanks to metal housing and connecting thread
- Fast troubleshooting thanks to an LED on each valve and diagnostics via fieldbus


## Easy to mount

- Fully assembled and tested valve terminal
- Less complicated when ordering, installing and commissioning
- Suitable for direct mounting even on moving system components

# Valve terminals type 80 CPV-SC, Smart Cubic

Key features

**FESTO**



## Equipment options

### Valve functions

- 5/2-way valve, single solenoid
- 5/2-way valve, double solenoid
- 3/2-way valve, normally open
- 3/2-way valve, normally closed
- 2/2-way valve, normally closed

### Separator plate with additional compressed air supply

- Compressed air channel (1) closed
- Compressed air channel (1) and exhaust duct (3/5) closed

### Blanking plate

- Plate without valve function for reserving a valve position

## Electrical connection options

### Individual connection

- 2 ... 16 valve positions/ max. 16 solenoid coils
- Individual connection, horizontal (H)
- Individual connection, vertical (T)

### Multi-pin plug

- 4 ... 16 valve positions/ max. 16 solenoid coils
- Sub-D
- Flat cable

### Fieldbus Direct

- 4 ... 16 valve positions/ max. 16 solenoid coils
- Profibus
- DeviceNet

### CP string extension

- Further valve terminals CPV-SC-CPI or from the CPV/CPA range
- Further valve terminals from the CPV/CPA range
- Electrical I/O modules

### CPI interface

- 4 ... 16 valve positions/ max. 16 solenoid coils

- Further valve terminals CPV-SC-CPI or from the CPV/CPA range

# Valve terminals type 80 CPV-SC, Smart Cubic

Key features

**FESTO**

## Valve terminal configurator

Online via: → [www.festo.com](http://www.festo.com)

Selecting a CPV-SC valve terminal using the online catalogue is quick and easy thanks to the convenient valve terminal configurator provided. This makes it much easier to order the right product. The valve terminals are assembled according to your order specifications and are individually tested. This reduces the assembly and installation time to a minimum. The valve terminal type 80 is ordered using the order code.



Ordering system for type 80

→ Internet: type 80

The illustration above provides an example of a valve terminal configuration. The following steps explain how you arrive at the order code:

Once you have called up → [www.festo.com](http://www.festo.com), click on “Automation” and select “Catalogue” from the “Products” submenu. Now select “Valve Terminals” and then “Universal Valve Terminals”.

Choose the valve terminal you want (CPV-SC in this case) and click on the link “Configure common options”. You can then configure the valve terminal step by step (from left to right) according to your requirements. Click on the shopping basket to save the selected configuration (this does not create an order).


You can switch to expert mode at any time by clicking on the “Further options” link. This provides you with extended options for configuring your valve terminal.

## 2D/3D CAD data

Online via: → [www.festo.com](http://www.festo.com)

You can request the CAD data for a valve terminal you have configured. To do so, perform the product search as described above. Go to the shopping basket and click on the CAD icon

(compass). On the next page you can generate a 3D preview or request another data format of your choice by e-mail.




# Valve terminals type 80 CPV-SC, Smart Cubic

Key features

**FESTO**

## Individual connection




Connection is independent of the control technology used and is flexible thanks to ready to install cables. This ensures correct polarity during installation.

Valves with integrated LED (CPVSC1-M1LH- ...) are available as an option for switching status display. Individual connection permits the selection of 2 to 16 solenoid coils (divided between 2 to 16 valve positions).

Variants

- Individual connection, horizontal
- Individual connection, vertical
- 2 to 16 solenoid coils

## Multi-pin plug connection




Control signals to the valve terminal are transmitted via a pre-assembled multi-core cable, which substantially reduces installation time.

The multi-pin plug connection enables the selection of 4 to 16 solenoid coils (divided between 2 to 16 valve positions).

Variants

- Sub-D connection
- Flat cable connection
- 4 to 16 solenoid coils

## Fieldbus Direct




An integrated fieldbus node manages the communication connection to a higher-order PLC. This enables a space-saving pneumatic and electronic solution.

The fieldbus connection enables the selection of 4 to 16 solenoid coils (divided between 4 to 16 valve positions).

Variants

- DeviceNet connection (CP functionality)
- Profibus connection (CPI functionality)
- 4 to 16 solenoid coils

## Fieldbus Direct with CP string extension



The optional string extension enables additional valve terminals and I/O modules to be connected to the fieldbus node of the CPV-SC. A CP string of the CPI installation system is integrated in the fieldbus node as an extension. Different input and output modules as well as CPV, MPA, CPV-SC, CPA valve terminals can be connected. The maximum length of the CP string extension is 10 metres, which means that the extension modules can be mounted directly on-site. All of the required electrical signals are transmitted via the CP cable, which in turn means that no further installation is needed on the extension module.

The CP string interface offers:

- Logic and sensor supply for the input modules
  - Load voltage supply for the valve terminals
  - Logic supply for the output modules
- With CP functionality:
- 16 input signals
  - 16 output signals for output modules 24 V DC or solenoid coils
- With CPI functionality:
- 32 input signals
  - 32 output signals for output modules 24 V DC or solenoid coils


➔ [www.festo.com](http://www.festo.com)

# Valve terminals type 80 CPV-SC, Smart Cubic

Key features

FESTO

## CPI installation system



Valve terminal for CPI installation system:

Valve terminals with CP connection are intended for connection to higher-order fieldbus nodes or to control blocks. A fieldbus node or control block also enables the connection of decentralised input/output units. The following fieldbus protocols are supported:

- Festo fieldbus, ABB CS31, Moeller Suconet K
- Interbus
- Allen Bradley (1771 RIO)
- DeviceNet
- Profibus DP, 12 MBd
- CC-Link
- Modbus/TCP
- Ethernet

Four strings with up to 32 inputs and outputs can be connected to a fieldbus node or control block. The connecting cables transmit the power supply for the input modules and the load voltage for the valves as well as control signals.

Further information

➔ Internet: cpi

# Valve terminals type 80 CPV-SC, Smart Cubic


Peripherals overview

FESTO

## Overview – CPV-SC valve terminal

Valve terminal with individual electrical connections

- Vertical individual connection  
Code: T
  - Horizontal individual connection  
Code: H
- Valve terminals with individual electrical connection can be equipped with 2 to max. 16 valve positions. Each valve position can either be equipped with a valve or a blanking plate.



- |   |   |  |                            |
|---|---|--|----------------------------|
| 1 Valve with vertical individual connection     | 4 Plug socket with cable for individual electrical connection of valves | 6 Tie rod  | 8 Inscription label holder |
| 2 Valve with horizontal individual connection   | 5 Left-hand end plate for compressed air supply 1 or 12/14              | 7 Sub-base for working ports (push-in fitting or threaded) | 9 Silencer                 |
| 3 Right-hand end plate for unducted exhaust air |   |  |                            |

# Valve terminals type 80 CPV-SC, Smart Cubic

Peripherals overview

FESTO


## Valve terminal with electrical multi-pin plug connection

- 15- and 26-pin Sub-D multi-pin plug connection  
Code: MS, MH
- or
- 20-pin multi-pin plug connection with connector for flat cable  
Code: MF

Valves and end plates are the basic pneumatic components of the valve terminal.  
The valve terminals are connected to the end plates using tie rods.

Valve terminals with electrical multi-pin plug connection can be equipped with 4 to max. 16 valve positions.  
Each valve position can either be equipped with a valve or a blanking plate.

The electrical connection is located on the left-hand side, thereby allowing flush mounting of the system.



- |   |  |  |                                       |
|---|--|--|---------------------------------------|
| 1 Electrical control unit (with LED switching status displays) for Sub-D plug or flat cable | 3 Right-hand end plate for ducted exhaust air or silencer (3/5 or 82/84) | 6 Cover for manual override (optional)                     | 9 Electrical valve linking module     |
| 2 Left-hand end plate for compressed air supply 1 or 12/14                                  | 4 Sub-base for ducted exhaust air (push-in fitting or threaded)          | 7 Sub-base for working ports (push-in fitting or threaded) | 10 Inscription label holder           |
|   | 5 Valve  | 8 Tie rod  | 11 H-rail mounting                    |
|   |  |  | 12 Blanking plate for vacant position |



# Valve terminals type 80 CPV-SC, Smart Cubic

Peripherals overview

## Valve terminal with Fieldbus Direct


- M12 A-coded DeviceNet connection  
Code: DN
- 9-pin Sub-D connection for Profibus  
Code: DP

Valves and end plates are the basic pneumatic components of the valve terminal.

The valve terminals are connected to the end plates using tie rods.

Valve terminals with Fieldbus Direct DeviceNet/Profibus DP can be equipped with 4 to max. 16 valve positions. Each valve position can either be equipped with a valve or a blanking plate.

The electrical connection is in the same direction as the tubing in order to save space.



- |   |  |   |  |
|---|--|---|--|
| <b>1</b> Fieldbus Direct  | <b>4</b> Sub-base for ducted exhaust air (push-in fitting or threaded) | <b>7</b> Sub-base for working ports (push-in fitting or threaded) | <b>10</b> Inscription label holder           |
| <b>2</b> Left-hand end plate for compressed air supply 1 or 12/14               | <b>5</b> Valve   | <b>8</b> Tie rod  | <b>11</b> H-rail mounting                    |
| <b>3</b> Right-hand end plate for ducted exhaust air or silencer (3/5 or 82/84) | <b>6</b> Cover for manual override (optional)                          | <b>9</b> Electrical valve linking module                          | <b>12</b> Blanking plate for vacant position |

# Valve terminals type 80 CPV-SC, Smart Cubic

Peripherals overview

FESTO


## Valve terminal with CPI connection

CP interface M9, 5-pin  
Code: CP

Valves and end plates are the basic pneumatic components of the valve terminal.  
The valve terminals are connected to the end plates using tie rods.

Valve terminals with CPI interface can be equipped with 4 to max. 16 valve positions. Each valve position can either be equipped with a valve or a blanking plate.

The electrical connection is in the same direction as the tubing in order to save space.



- |   |  |   |  |
|---|--|---|--|
| <b>1</b> CPI connection   | <b>4</b> Sub-base for ducted exhaust air (push-in fitting or threaded) | <b>7</b> Sub-base for working ports (push-in fitting or threaded) | <b>10</b> Inscription label holder           |
| <b>2</b> Left-hand end plate for compressed air supply 1 or 12/14               | <b>5</b> Valve   | <b>8</b> Tie rod  | <b>11</b> H-rail mounting                    |
| <b>3</b> Right-hand end plate for ducted exhaust air or silencer (3/5 or 82/84) | <b>6</b> Cover for manual override (optional)                          | <b>9</b> Electrical valve linking module                          | <b>12</b> Blanking plate for vacant position |

# Valve terminals type 80 CPV-SC, Smart Cubic

Key features – Pneumatic components

FESTO








## Valves

CPVSC1 valves are valves with integrated sub-base, i.e. in addition to the valve function they contain all of the ducts for supply, exhaust and the

working ports. The supply ducts are a central component of the valve slices and enable a direct flow of air. This helps achieve maximum flow rates. All

valves have a pneumatic pilot control for optimising performance. The valve function is based on a piston spool system with a patented sealing prin-

ciple that guarantees its suitability for a wide range of applications as well as a long service life.

Valve functions	Code	Circuit symbol	Width 10 mm	Description
	M		■	5/2-way single solenoid valve • Pneumatic spring return
	N		■	3/2-way single solenoid valve • Normally open • Pneumatic spring return
	K		■	3/2-way single solenoid valve • Normally closed • Pneumatic spring return
	D		■	2/2-way single solenoid valve • Normally closed • Pneumatic spring return
	J		■	5/2-way double solenoid valve This valve consists of two valve housing units and therefore occupies two valve positions. The pilot control with coil 12 is located on the left and labelled "J12". If both coils are actuated, the signal at port "14" dominates in switching position.









-  - Note

For vacuum operation valves require a filter. This is to avoid that foreign matter is drawn into the valve (e.g. when using a suction cup).

# Valve terminals type 80 CPV-SC, Smart Cubic

FESTO

Key features – Pneumatic components

Valves				
Valve functions	Code	Circuit symbol	Width 10 mm	Description
Pneumatic supply plate with duct separation				
	T		■	Compressed air channel (1) closed For separating pressure zones with a common exhaust. (Using pressure zones → 14) Pneumatic connection: QS-4, M5
	S		■	Compressed air channel (1) and exhaust duct (3/5) closed For separating pressure zones with a separate exhaust. (Using pressure zones → 14) Pneumatic connection: QS-4, M5
Pneumatic supply plate without duct separation				
	U		■	Additional compressed air supply (1) and additional exhaust (3/5). Pneumatic connection: QS-4, M5
Blanking plate				
	L		■	Plate without valve function for reserving a valve position. No pneumatic connection


In the case of compressed air supply configuration code S or T (exhausting via flat plate silencer), a plug-in silencer UC-QS-4H is included with supply plates.

# Valve terminals type 80 CPV-SC, Smart Cubic

Key features – Pneumatic components

FESTO

## Constructional design



### Valve replacement

Valves can be replaced quickly and easily in just a few movements. Separating seals between the valves are based on a metal support and are secured in place.

### Extension

Valves can be ordered as accessories and are available with fully assembled sub-bases with QS or threaded connections. The functionality of the valve terminal can therefore be extended by equipping vacant positions.

For ordering purposes, valves have the valve code printed on the front and the product type on the back.

### Materials

The valve housing and thread in the sub-bases are metallic, while other housing sections are made from robust plastic materials.



Note

The valve with the working sub-base has been tested by Festo for leak tightness.

## Pilot air supply

The port for the main pneumatic supply is located on the left-hand end plate.

The ports differ for the following types of pilot air supply:

- Internal
- External

### Internal pilot air supply

An internal pilot air supply can be selected if the terminal is working in an operating pressure range between 3 and 7<sup>1)</sup> bar.

The pilot air supply in the left-hand end plate is then branched from the compressed air supply 1 using an internal connection. The port 12/14 is closed using a blanking plug.

### External pilot air supply

If the terminal is working in an operating pressure range from –0.9 to 3 bar, you must operate your CPV-SC valve terminal using an external pilot air supply. The pilot air supply is also supplied via port 12/14 on the left-hand end plate in this case.

1) 8 bar upon request

## Creation of pressure zones and separation of exhaust air

The CPV-SC valve terminal can be operated with multiple pressure zones. After two zones, a supply with duct separation is required for each subsequent pressure zone. It always

occupies one valve position. An isolating disc T separates the compressed air supply of a valve group on the left from the compressed air supply of a valve group on the right. The right-

hand pressure zone is supplied at port 4 of the supply plate. Port 2 also allows the left-hand pressure zone to be exhausted. All of the exhaust ducts of the valve are interconnected and

are exhausted through the right-hand end plate. An isolating disc S also separates exhaust ducts 3 and 5 in addition to pressure duct 1.



Note

Larger or simultaneously operating cylinders generate a back pressure in the exhaust duct of the valve terminal, the level of which depends on the exhaust capacity of the silencer.

In order to prevent interaction with adjacent valves, valves can be separated by means of duct separation using isolating disc S. The pressure zone located to the left of an isolating



disc S is exhausted using the supplied plug-in silencer. Where there are more than two valves in such a pressure zone, an additional supply with additional exhaust may be required.





It is therefore useful to meet the higher exhaust requirements in the pressure zone that is exhausted by the right-hand end plate.

# Valve terminals type 80 CPV-SC, Smart Cubic

FESTO

Key features – Pneumatic components

Creating pressure zones		
	Code	Description
	S	Duct 1 and 3/5 separated
	T	Duct 1 separated

Pneumatic working ports		
	Code	Description
Working port		
	B	M5 threaded connection
	E	QS-3 push-in connector
	F	QS-4 push-in connector
Supply port, left-hand end plate		
	C	Threaded connection <ul style="list-style-type: none"> <li>• M7 (internal pilot air supply)</li> <li>• M5 and M7 (external pilot air supply)</li> </ul>
	G	Push-in connection <ul style="list-style-type: none"> <li>• QS-6 (internal pilot air supply)</li> <li>• QS-4 and QS-6 (external pilot air supply)</li> </ul>

## Valve terminals type 80 CPV-SC, Smart Cubic

Key features – Pneumatic components

**FESTO**

### Ports for supply and exhaust




#### Supply and exhaust

A basic feature of a CPV-SC valve terminal are the two end plates.

The left-hand end plate is used to supply compressed air, while the right-hand end plate is used to exhaust the valve terminal.

Exhaust air escapes either via an integrated flat plate silencer, round silencer or via a push-in or threaded connection.







### Ports for exhaust

	Code	Description
	S	<ul style="list-style-type: none"> <li>Internal pilot air supply</li> <li>Exhaust from duct 3/5 as well as 82/84 is via a flat plate silencer</li> <li>Replacement part (insert) for flat plate silencer: Type CPVSC1-UA</li> </ul>
	T	<ul style="list-style-type: none"> <li>External pilot air supply</li> <li>Exhaust from duct 3/5 as well as 82/84 is via a flat plate silencer</li> <li>Replacement part (insert) for flat plate silencer: Type CPVSC1-UA</li> </ul>
	V	<ul style="list-style-type: none"> <li>Internal pilot air supply</li> <li>Exhaust from duct 3/5 as well as 82/84 is via ducted exhaust air</li> </ul>
	X	<ul style="list-style-type: none"> <li>External pilot air supply</li> <li>Exhaust from duct 3/5 as well as 82/84 is via ducted exhaust air</li> </ul>
	Y	<ul style="list-style-type: none"> <li>Internal pilot air supply</li> <li>Exhaust from duct 3/5 as well as 82/84 is via a round silencer</li> </ul>
	Z	<ul style="list-style-type: none"> <li>External pilot air supply</li> <li>Exhaust from duct 3/5 as well as 82/84 is via a round silencer</li> </ul>

## Valve terminals type 80 CPV-SC, Smart Cubic

Key features – Pneumatic components

**FESTO**

Pneumatic supply		
End plate combination	Code	Description
	S	<p>Internal pilot air supply, flat plate silencer</p> <p>For operating pressure in the range 3 ... 7 bar</p>
	T	<p>External pilot air supply, flat plate silencer</p> <p>For operating pressure in the range -0.9 ... +7 bar</p>
	V	<p>Internal pilot air supply, ducted exhaust air</p> <p>For operating pressure in the range 3 ... 7 bar</p>
	X	<p>External pilot air supply, ducted exhaust air</p> <p>For operating pressure in the range -0.9 ... +7 bar</p>
	Y	<p>Internal pilot air, round silencer</p> <p>For operating pressure in the range 3 ... 7 bar</p>
	Z	<p>External pilot air supply, round silencer</p> <p>For operating pressure in the range -0.9 ... +7 bar</p>




# Valve terminals type 80 CPV-SC, Smart Cubic

Key features – Electrical components

**FESTO**

## Protective circuit



Each solenoid coil is protected with a spark arresting protection circuit as well as against polarity reversal.

## Electrical multi-pin plug connection

The following multi-pin plug connection types are offered for the valve terminal CPV-SC:


- Sub-D multi-pin plug connection (15- and 26-pin) or
- Multi-pin plug connection with connector for flat cable (20-pin)

CPV-SC is connected via a multi-pin plug connection with Sub-D or flat cable. Each pin of the multi-pin plug is assigned a maximum of one valve position and therefore one coil or one address.

Double solenoid valves “J” occupy two valve positions. The left-hand valve position with pilot control 12 is actuated by the less significant of the two addresses.


## Electrical multi-pin plug connection – Sub-D

Code MS, MH



With this electrical connection variant, all valves are centrally actuated via the 15 and 26-pin connector plug. The electrical connection is located on the left-hand side.



## Ordering data – Connecting cable Sub-D

	Code	Description	Type	Part No.	
	CP	15-pin for 12 coils (code MS)	2.5 m long	KMP6-15P-12-2,5	527 543
	CQ	Material: PVC	5 m long	KMP6-15P-12-5	527 544
	CR	Suitable for chain link trunking	10 m long	KMP6-15P-12-10	527 545
	CP	26-pin for 16 coils (code MH)	2.5 m long	KMP6-26P-16-2,5	527 546
	CQ	Material: PVC	5 m long	KMP6-26P-16-5	527 547
	CR	Suitable for chain link trunking	10 m long	KMP6-26P-16-10	527 548



# Valve terminals type 80 CPV-SC, Smart Cubic

Key features – Electrical components

**FESTO**

Pin allocation for 15-pin Sub-D (code MS)				
KMP6-15P-12-...	Description	Pin	Core colour	Address/coil
	Plug socket with cable for the CPV-SC valve terminal with up to 12 valve positions	1	White	Coil 0
		2	Brown	Coil 1
		3	Green	Coil 2
		4	Yellow	Coil 3
		5	Grey	Coil 4
		6	Pink	Coil 5
		7	Blue	Coil 6
		8	Red	Coil 7
		9	Black	Coil 8
	 Note The drawing shows a plan view of the Sub-D socket on the multi-pin cable KMP6-15P-12-....	10	Purple	Coil 9
		11	Grey-pink	Coil 10
		12	Red-blue	Coil 11
		13	White-green	n.c.
		14	Brown-green	0 V <sup>1)</sup>
		15	White-yellow	0 V <sup>1)</sup>

- 1) Pin 14 to pin 15 are bridged in the valve terminal.  
0 V for positive switching control signals; 24 V can be connected for negative switching control signals.


Pin allocation for 26-pin Sub-D (code MH)				
KMP6-26P-16-...	Description	Pin	Core colour	Allocation
	Plug socket with cable for the CPV-SC valve terminal with 16 valve positions	1	White	Coil 0
		2	Brown	Coil 1
		3	Green	Coil 2
		4	Yellow	Coil 3
		5	Grey	Coil 4
		6	Pink	Coil 5
		7	Blue	Coil 6
		8	Red	Coil 7
		9	Black	Coil 8
		10	Purple	Coil 9
		11	Grey-pink	Coil 10
		12	Red-blue	Coil 11
		13	White-green	Coil 12
		14	Brown-green	Coil 13
		15	White-yellow	Coil 14
		16		Coil 15
		17		Coil 16
		18		n.c.
		19		n.c.
		20		0 V <sup>1)</sup>
	 Note The drawing shows a plan view of the Sub-D socket on the multi-pin cable KMP6-26P-12-....	21		0 V <sup>1)</sup>
		22		0 V <sup>1)</sup>
		23	White-grey	0 V <sup>1)</sup>
		24	Grey-brown	0 V <sup>1)</sup>
		25	White-pink	0 V <sup>1)</sup>
		26	Pink-brown	0 V <sup>1)</sup>

- 1) Pin 17 to pin 22 are bridged in the valve terminal.  
0 V for positive switching control signals; 24 V can be connected for negative switching control signals.


# Valve terminals type 80 CPV-SC, Smart Cubic

Key features – Electrical components

Electrical multi-pin plug connection – Connector for flat cable  
Code MF



With this electrical connection variant, all valves are centrally actuated via the 20-pin connector plug. The electrical connection is located on the left-hand side.

Pin allocation – Connector for flat cable (code MF)		
	Pin	Allocation
	1	Coil 0
	2	Coil 1
	3	Coil 2
	4	Coil 3
	5	Coil 4
	6	Coil 5
	7	Coil 6
	8	Coil 7
	9	Coil 8
	10	Coil 9
	11	Coil 10
	12	Coil 11
	13	Coil 12
	14	Coil 13
	15	Coil 14
	16	Coil 15
	17	0 V <sup>1)</sup>
	18	0 V <sup>1)</sup>
	19	0 V <sup>1)</sup>
	20	0 V <sup>1)</sup>
CPV-SC valve terminal with up to 16 valve positions and 20-pin multi-pin socket for flat cables to DIN 41561-1, -2 or IEC 60603-13-C020FD-7C1E-2G  Contact surface gold Flat cable grid 1.27 mm Conductor cross section 0.13 mm <sup>2</sup>		

1) Pin 17 to pin 20 are bridged in the valve terminal.


# Valve terminals type 80 CPV-SC, Smart Cubic

Key features – Electrical components


FESTO

## Fieldbus Direct

DeviceNet



Profibus DP



## Properties


Fieldbus Direct is a system for the compact connection of a valve terminal of various sizes to different fieldbus standards.

The CP string extension option allows the functions and components of the CPI installation system to be used.

The I/O modules and cables for the CP string extension are ordered using the order code for the CPI installation system.

➔ Internet: cpi


## Fieldbus connection CP




All CP valve terminals and CP modules are connected using a ready to install CP cable, and are attached to the CP interface. Four modules, for example one CPV-SC valve terminal and one to three CP input modules, make up an installation string that ends at the CP

interface. The installation system supports a maximum of 4 installation strings, which can be connected to a CP fieldbus node.

The CP interface of CPV-SC is represented in the CP/CPI system by a module with 16 outputs.

 **Note**  
Further information can be found in  
➔ Internet: cpi

## Address allocation – Solenoid coils



**1** Single solenoid valves occupy one valve position

**2** Double solenoid valves occupy two valve positions

## Example:

Valve terminal where valve positions 5 and 6 are prepared for double solenoid valves.

The addresses of the valve positions on the CPV-SC-DN/CPV-SC-DP are assigned from left to right. Each valve position has an address, regardless of whether or not a valve is mounted there.

Double solenoid valves “J” occupy two valve positions. The left-hand valve position with pilot control 12 is actuated by the less significant of the two addresses.

# Valve terminals type 80 CPV-SC, Smart Cubic

Key features – Display and operation

FESTO

## Display and operation

The switching status of every solenoid coil is displayed on the control unit LED. Inscription labels (type MH-BZ-80x) can be applied to each valve for labelling purposes.

The manual override (MO) allows the valve to be activated without electronic control or power supply. The valve is activated by pushing the manual override. The set switching status can also be secured by rotating the manual override.


A cover can be fitted over the manual override to prevent it from being activated accidentally (code V).



Note


A manually activated valve (manual override) cannot be reset electrically. Conversely, an electrically activated valve cannot be reset using the manual override facility.

## Manual override (MO)




- 1 Manual override (non-detenting or detenting via turning using a screwdriver)
- 2 Cover for manual override (code V)
- 3 Location for valve position inscription label (type MH-BZ-80x)
- 4 Numbering of valve positions
- 5 LED signal status display per valve position

## Manual override with automatic return (non-detenting)



Manual override is actuated by pushing it with a pointed object or screwdriver and reset by spring force.

## Manual override set via turning (detenting)



Manual override remains active until it is reset with a screwdriver.


# Valve terminals type 80 CPV-SC, Smart Cubic

Key features – Display and operation

FESTO


## Display and operation

Fieldbus Direct – DeviceNet




- 1 Connection for CP extension (with CP functionality)
- 2 Connection for power supply
- 3 Connection for fieldbus
- 4 DIL switch for CP extension
- 5 Rotary switch for baud rate
- 6 Rotary switch for station number
- 7 Earth terminal
- 8 Cover (for IP40 protection)
- 9 Switching status display per valve

Fieldbus Direct – Profibus DP



- 1 Connection for CP extension (with CPI functionality)
- 2 Connection for power supply
- 3 Connection for fieldbus
- 4 DIL switch for CP extension
- 5 Rotary switch for station number
- 6 Earth terminal
- 7 Cover (for IP40 protection)
- 8 Switching status display per valve

CP interface




- 1 Status LEDs for valves
- 2 Status LED for CP communication
- 3 CP connection, incoming
- 4 CP connection, outgoing
- 5 Earth terminal

## Valve terminals type 80 CPV-SC, Smart Cubic

Key features – Display and operation


FESTO

### Inscription label holder



The transparent inscription label holder provides sufficient space for individually created labels on paper or foil.

Labelling templates are available on  
➔ [www.festo.com](http://www.festo.com)



# Valve terminals type 80 CPV-SC, Smart Cubic

FESTO


Key features – Mounting types

## Mounting – Valve terminal

Sturdy terminal mounting thanks to:


- Four through-holes for wall mounting
- H-rail mounting

### Wall mounting




1 Mounting holes for screws M3

### H-rail mounting



The mounting CPVSC1-HS35 facilitates mounting on a H-rail to EN 60715.



The CPV-SC valve terminal is attached to the H-rail (see arrow A).

The valve terminal is then swivelled on the H-rail and secured in place with the clamping component (see arrow B).




- 1 Holes for wall mounting
- 2 Self-tapping M4x10 screw of the H-rail clamping unit
- 3 Clamping component of the H-rail clamping unit



## Valve terminals type 80 CPV-SC, Smart Cubic

FESTO

Technical data

-  - Flow rate  
170 l/min
-  - Valve width  
10 mm
-  - Voltage  
5, 12, 24 V DC




General technical data					
Valve	5/2-way valve		3/2-way valve		2/2-way valve
	Single solenoid	Double solenoid	Normally open	Normally closed	Normally closed
Valve function order code	M	J	N	K	D
Constructional design	Electromagnetically actuated piston spool valve				
Width [mm]	10		10		10
Nominal diameter [mm]	2.5		2.5		2.5
Standard nominal flow rate [l/min]	170		170		150
Lubrication	Life-time lubrication				
Type of mounting	Wall mounting				
Mounting position	Any				
Manual override	Non-detenting/detenting/blocked				
Pneumatic connections					
Supply	1	M7, QS-6			
Exhaust port	3/5	M7, QS-6, round silencer or integrated flat plate silencer			
Working ports	2/4	Depending on the connection type selected <ul style="list-style-type: none"><li>• M5</li><li>• QS-3</li><li>• QS-4</li></ul>			
Pilot air port	12/14	M5, QS-4			
Pilot exhaust air port	82/84	M5, QS-4, round silencer or integrated flat plate silencer			

# Valve terminals type 80 CPV-SC, Smart Cubic

Technical data

FESTO

Pilot pressure p2 as a function of operating pressure p1



1 Operating range for valves with external pilot air

Valve response times [ms]

Valve function order code		M	J	N	K	D
Response times	on	10	10	10	10	10
	off	10	–	10	10	10
	changeover	–	8	–	–	–

Operating and environmental conditions

Valve function order code		M	J	N	K	D
Operating medium		Filtered compressed air, lubricated or unlubricated, inert gases permissible → 28				
Grade of filtration	[µm]	40				
Paint-wetting impairment substances criterion		Yes (free of paint-wetting impairment substances)				
CE certification		Yes, with control unit to EMC regulations				
Certification		cULus recognized (OL)				
Operating pressure	bar]	–9 ... +7				
Operating pressure for valve terminal with internal pilot air supply	bar]	3 ... 7				
Pilot pressure	bar]	3 ... 7				
Ambient temperature	[°C]	–5 ... +50				
Temperature of medium	[°C]	–5 ... +50				
Storage temperature	[°C]	–20 ... +40				
Corrosion resistance class CRC <sup>1)</sup>		1				

1) Corrosion resistance class 1 according to Festo standard 940 070

Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

# Valve terminals type 80 CPV-SC, Smart Cubic

FESTO

Technical data

Electrical data							
Valve function order code			M	J	N	K	D
Electromagnetic compatibility of the CPV-SC valve terminal with Sub-D or flat cable connection			Interference emission tested to DIN EN 61000-6-4, industry				
			Interference immunity <sup>1)</sup> tested to DIN EN 61000-6-2, industry				
Protection against electric shock (protection against direct and indirect contact to EN 60204-1/IEC 204)			By means of PELV power supply unit				
Nominal operating voltage of valve terminal	Multi-pin plug connection	[V DC]	24				
	Individual sub-base	[V]	5 , 12, 22, 24				
Permissible voltage fluctuations		[%]	±10				
Coil characteristics	Nominal voltage	[V DC]	5 , 12, 22, 24				
	Electrical power consumption	[W]	1				
Duty cycle			100% at 40°C ambient temperature				
Protection class to EN 60529			IP40 (in assembled state and with detenting plug)				
Relative air humidity		[%]	90 at 40 °C, non-condensing				

1) The maximum signal line length is 10 m

Materials					
Valve function order code	M	J	N	K	D
Electrical interface	Polymer				
End plate, electrical sub-base	Polymer				
Seals	Elastomer				
Valve slice	Die-cast aluminium				
Sub-base for working ports	Polyamide				

Product weight [g]					
Valve function order code	M	J	N	K	D
5/2-way, 3/2-way valve	30.5				
5/2-way double solenoid valve	56.5				
Blanking plate	22.5				
Right-hand end plate	42.5				
Left-hand end plate	28				
Actuator housing	43				
Tie rod, 16-fold	29.6				
Electrical manifold module, 16-fold	64				
Control unit (fieldbus)	200				
Electrical interface CPI	150				

# Valve terminals type 80 CPV-SC, Smart Cubic

Technical data

FESTO

## Equipment

Operate your equipment with unlubricated compressed air if possible.

Festo valves and cylinders are designed so that, if used as designated, they will not require additional lubrication and will still achieve a long service life.

The quality of compressed air downstream from the compressor must correspond to that of unlubricated compressed air. If possible, do not operate all of your equipment with lubricated compressed air. The lubricators should, where possible, always be installed directly upstream of the cylinders used.

Incorrect additional oil and too high an oil content in the compressed air reduces the service life of a valve terminal.

Use Festo special oil OFSW-32 or the alternatives listed in the Festo catalogue (as specified in DIN 51524 HLP32; basic oil viscosity 32 CST at 40°C).

### Bio-oils

When using bio-oils (oils which are based upon synthetic or native ester, e.g. rapeseed oil methyl ester), the maximum residual oil content of 0.1 mg/m<sup>3</sup> must not be exceeded (see ISO 8573-1 Class 2).

### Mineral oils

When using mineral oils (e.g. HLP oils to DIN 51524, Parts 1 to 3) or similar oils based on poly-alpha-olefins (PAO), the maximum residual oil content of 5 mg/m<sup>3</sup> must not be exceeded (see ISO 8573-1 Class 4).

A higher residual oil content irrespective of the compressor oil cannot be permitted, as the basic lubricant would be flushed out over time.

# Valve terminals type 80 CPV-SC, Smart Cubic


Technical data

**FESTO**

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

With individual connection



1 QS push-in fitting

Valve positions n	L1	L2	L3
2	71.4	62.5	21
3	81.9	73	31.5
4	92.4	83.5	42
5	102.9	94	52.5
6	113.4	104.5	63
7	123.9	115	73.5
8	134	125.1	84
9	144.9	136	94.5
10	155.4	146.5	105
11	165.9	157	115.5
12	176.4	167.5	126
13	186.9	178	136.5
14	197.4	188.5	147
15	207.9	199	157.5
16	218.4	209.5	168

# Valve terminals type 80 CPV-SC, Smart Cubic


Technical data

FESTO

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

With multi-pin plug connection



Valve positions n	L1	L2	L3
2	104	93	21
3	114.5	103.5	31.5
4	125	114	42
5	135.5	124.5	52.5
6	146	135	63
7	146.5	145.5	73.5
8	167	156	84
9	177.5	166.5	94.5
10	188	177	105
11	198.5	187.5	115.5
12	209	198	126
13	219.5	208.5	136.5
14	230	219	147
15	240.5	229.5	157.5
16	251	240	168

# Valve terminals type 80 CPV-SC, Smart Cubic

Technical data



Dimensions – Sub-D plug with cable

Download CAD data → [www.festo.com](http://www.festo.com)

1 15-/26-pin plug

Type	B1	D1	H1	L1	L2			Number of pins
KMP6-15P-12-...	16	8.5	40	34.5	2,500	5,000	10,000	15
KMP6-26P-16-...	16	8.6	40	34.5	2,500	5,000	10,000	26

# Valve terminals type 80 CPV-SC, Smart Cubic


FESTO

Technical data

## Dimensions – Valve terminal

Download CAD data → [www.festo.com](http://www.festo.com)

With fieldbus connection



- 1 QS push-in fitting
- 2 Cover cap
- 3 DeviceNet fieldbus connection  
(dimensions for Profibus DP  
are identical with the exception  
of the bus connection)
- 4 Bus connection M12
- 5 Power supply M12
- 6 CP connection M9

Valve positions n	L1	L2	L3	L4
2	162.6	151.8	21	164.4
3	173.1	162.3	31.5	174.9
4	183.6	172.8	42	185.4
5	194.1	183.3	52.5	195.9
6	204.6	193.8	63	206.4
7	215.1	204.3	73.5	216.9
8	225.6	214.8	84	227.4
9	236.1	225.3	94.5	237.9
10	246.6	235.8	105	248.4
11	257.1	246.3	115.5	258.9
12	267.6	256.8	126	269.4
13	278.1	267.3	136.5	279.9
14	288.6	277.8	147	290.4
15	299.1	288.3	157.5	300.9
16	309.6	298.8	168	311.4



# Valve terminals type 80 CPV-SC, Smart Cubic


Technical data

**FESTO**

## Dimensions – Valve terminal

Download CAD data → [www.festo.com](http://www.festo.com)

With CPI interface








Valve positions n	L1	L2	L3	L4
2	133.9	123.1	21	135.7
3	144.4	133.6	31,5	146.2
4	154.9	144.1	42	156.7
5	165.4	154.6	52,5	167.2
6	175.9	165.1	63	177.7
7	186.4	175.6	73,5	188.2
8	196.9	186.1	84	198.7
9	207.4	196.6	94,5	209.2
10	217.9	207.1	105	219.7
11	228.4	217.6	115,5	230.2
12	238.9	228.1	126	240.7
13	249.4	238.6	136,5	251.2
14	259.9	249.1	147	261.7
15	270.4	259.6	157,5	272.2
16	280.9	270.1	168	282.7

## Valve terminals type 80 CPV-SC, Smart Cubic

Accessories


**FESTO**

Ordering data – Valves with electrical plug-in connection			
Designation		Type	Part No.
 	Solenoid valve with M5 connections		
	5/2-way single solenoid valve	CPVSC1-M1H-M-P-M5	527 550
	5/2-way double solenoid valve	CPVSC1-M1H-J-P-M5	527 553
	3/2-way valve, normally open	CPVSC1-M1H-N-P-M5O	527 551
	3/2-way valve, normally closed	CPVSC1-M1H-K-P-M5C	527 552
	2/2-way valve, normally closed	CPVSC1-M1H-D-P-M5C	527 554
	Solenoid valve with QS-3 push-in connectors		
	5/2-way single solenoid valve	CPVSC1-M1H-M-P-Q3	527 555
	5/2-way double solenoid valve	CPVSC1-M1H-J-P-Q3	527 558
	3/2-way valve, normally open	CPVSC1-M1H-N-P-Q3O	527 556
	3/2-way valve, normally closed	CPVSC1-M1H-K-P-Q3C	527 557
	2/2-way valve, normally closed	CPVSC1-M1H-D-P-Q3C	527 559
	Solenoid valve with QS-4 push-in connectors		
	5/2-way single solenoid valve	CPVSC1-M1H-M-P-Q4	527 560
	5/2-way double solenoid valve	CPVSC1-M1H-J-P-Q4	527 563
	3/2-way valve, normally open	CPVSC1-M1H-N-P-Q4O	527 561
	3/2-way valve, normally closed	CPVSC1-M1H-K-P-Q4C	527 562
	2/2-way valve, normally closed	CPVSC1-M1H-D-P-Q4C	527 564
	Blanking plates with integrated connections		
	Vacant position, with blanking plate	CPVSC1-RP-B	527 527
	Supply plate M5		
	Duct 1 separated	CPVSC1-SP-P-M5	527 528
	Duct 1/3/5 separated	CPVSC1-SP-PRS-M5	527 530
	Without duct separation	CPVSC1-SP-M5	527 532
	Supply plate, QS-4 push-in connector		
	Duct 1 separated	CPVSC1-SP-P-Q4	527 529
	Duct 1/3/5 separated	CPVSC1-SP-PRS-Q4	527 531
	Without duct separation	CPVSC1-SP-Q4	527 533
		Cover for manual override	
Non-detenting, 10 pieces		VMPA-HBV-B	540 898

# Valve terminals type 80 CPV-SC, Smart Cubic

Accessories



**FESTO**

Ordering data – Valves with individual electrical connection, detenting manual override, vertical plug, 24 V DC			
Designation		Type	Part No.
	Solenoid valve with M5 connections		
	5/2-way single solenoid valve	CPVSC1-M1H-M-T-M5	547 276
	5/2-way double solenoid valve	CPVSC1-M1H-J-T-M5	547 277
	3/2-way valve, normally open	CPVSC1-M1H-N-T-M50	547 275
	3/2-way valve, normally closed	CPVSC1-M1H-K-T-M5C	547 274
	2/2-way valve, normally closed	CPVSC1-M1H-D-T-M5C	547 273
	Solenoid valve with M5 connections and LED		
	5/2-way single solenoid valve	CPVSC1-M1LH-M-T-M5	547 306
	5/2-way double solenoid valve	CPVSC1-M1LH-J-T-M5	547 307
	3/2-way valve, normally open	CPVSC1-M1LH-N-T-M50	547 305
	3/2-way valve, normally closed	CPVSC1-M1LH-K-T-M5C	547 304
	2/2-way valve, normally closed	CPVSC1-M1LH-D-T-M5C	547 303
	Solenoid valve with QS-3 push-in connectors		
	5/2-way single solenoid valve	CPVSC1-M1H-M-T-Q3	547 281
	5/2-way double solenoid valve	CPVSC1-M1H-J-T-Q3	547 282
	3/2-way valve, normally open	CPVSC1-M1H-N-T-Q30	547 280
3/2-way valve, normally closed	CPVSC1-M1H-K-T-Q3C	547 279	
2/2-way valve, normally closed	CPVSC1-M1H-D-T-Q3C	547 278	
Solenoid valve with QS-3 push-in connectors and LED			
5/2-way single solenoid valve	CPVSC1-M1LH-M-T-Q3	547 311	
5/2-way double solenoid valve	CPVSC1-M1LH-J-T-Q3	547 312	
3/2-way valve, normally open	CPVSC1-M1LH-N-T-Q30	547 310	
3/2-way valve, normally closed	CPVSC1-M1LH-K-T-Q3C	547 309	
2/2-way valve, normally closed	CPVSC1-M1LH-D-T-Q3C	547 308	
Solenoid valve with QS-4 push-in connectors			
5/2-way single solenoid valve	CPVSC1-M1H-M-T-Q4	547 286	
5/2-way double solenoid valve	CPVSC1-M1H-J-T-Q4	547 287	
3/2-way valve, normally open	CPVSC1-M1H-N-T-Q40	547 285	
3/2-way valve, normally closed	CPVSC1-M1H-K-T-Q4C	547 284	
2/2-way valve, normally closed	CPVSC1-M1H-D-T-Q4C	547 283	
Solenoid valve with QS-4 push-in connectors and LED			
5/2-way single solenoid valve	CPVSC1-M1LH-M-T-Q4	547 316	
5/2-way double solenoid valve	CPVSC1-M1LH-J-T-Q4	547 317	
3/2-way valve, normally open	CPVSC1-M1LH-N-T-Q40	547 315	
3/2-way valve, normally closed	CPVSC1-M1LH-K-T-Q4C	547 314	
2/2-way valve, normally closed	CPVSC1-M1LH-D-T-Q4C	547 313	

# Valve terminals type 80 CPV-SC, Smart Cubic

Accessories


FESTO


Ordering data – Valves with individual electrical connection, detenting manual override, horizontal plug, 24 V DC			
Designation		Type	Part No.
 	Solenoid valve with M5 connections		
	5/2-way single solenoid valve	CPVSC1-M1H-M-H-M5	547 291
	5/2-way double solenoid valve	CPVSC1-M1H-J-H-M5	547 292
	3/2-way valve, normally open	CPVSC1-M1H-N-H-M50	547 290
	3/2-way valve, normally closed	CPVSC1-M1H-K-H-M5C	547 289
	2/2-way valve, normally closed	CPVSC1-M1H-D-H-M5C	547 288
	Solenoid valve with M5 connections and LED		
	5/2-way single solenoid valve	CPVSC1-M1LH-M-H-M5	547 322
	5/2-way double solenoid valve	CPVSC1-M1LH-J-H-M5	547 323
	3/2-way valve, normally open	CPVSC1-M1LH-N-H-M50	547 321
	3/2-way valve, normally closed	CPVSC1-M1LH-K-H-M5C	547 320
	2/2-way valve, normally closed	CPVSC1-M1LH-D-H-M5C	547 318
	Solenoid valve with QS-3 push-in connectors		
	5/2-way single solenoid valve	CPVSC1-M1H-M-H-Q3	547 296
	5/2-way double solenoid valve	CPVSC1-M1H-J-H-Q3	547 297
	3/2-way valve, normally open	CPVSC1-M1H-N-H-Q30	547 295
3/2-way valve, normally closed	CPVSC1-M1H-K-H-Q3C	547 294	
2/2-way valve, normally closed	CPVSC1-M1H-D-H-Q3C	547 293	
Solenoid valve with QS-3 push-in connectors and LED			
5/2-way single solenoid valve	CPVSC1-M1LH-M-H-Q3	547 327	
5/2-way double solenoid valve	CPVSC1-M1LH-J-H-Q3	547 328	
3/2-way valve, normally open	CPVSC1-M1LH-N-H-Q30	547 326	
3/2-way valve, normally closed	CPVSC1-M1LH-K-H-Q3C	547 325	
2/2-way valve, normally closed	CPVSC1-M1LH-D-H-Q3C	547 324	
Solenoid valve with QS-4 push-in connectors			
5/2-way single solenoid valve	CPVSC1-M1H-M-H-Q4	547 301	
5/2-way double solenoid valve	CPVSC1-M1H-J-H-Q4	547 302	
3/2-way valve, normally open	CPVSC1-M1H-N-H-Q40	547 300	
3/2-way valve, normally closed	CPVSC1-M1H-K-H-Q4C	547 299	
2/2-way valve, normally closed	CPVSC1-M1H-D-H-Q4C	547 298	
Solenoid valve with QS-4 push-in connectors and LED			
5/2-way single solenoid valve	CPVSC1-M1LH-M-H-Q4	547 332	
5/2-way double solenoid valve	CPVSC1-M1LH-J-H-Q4	547 333	
3/2-way valve, normally open	CPVSC1-M1LH-N-H-Q40	547 331	
3/2-way valve, normally closed	CPVSC1-M1LH-K-H-Q4C	547 330	
2/2-way valve, normally closed	CPVSC1-M1LH-D-H-Q4C	547 329	

# Valve terminals type 80 CPV-SC, Smart Cubic

Accessories

**FESTO**


Ordering data – Valves with individual electrical connection, pushing manual override, vertical plug, 24 V DC			
Designation		Type	Part No.
	Solenoid valve with M5 connections		
	5/2-way single solenoid valve	CPVSC1-M1HT-M-T-M5	548 037
	5/2-way double solenoid valve	CPVSC1-M1HT-J-T-M5	548 038
	3/2-way valve, normally open	CPVSC1-M1HT-N-T-M50	548 036
	3/2-way valve, normally closed	CPVSC1-M1HT-K-T-M5C	548 035
	2/2-way valve, normally closed	CPVSC1-M1HT-D-T-M5C	548 034
	Solenoid valve with QS-3 push-in connectors		
	5/2-way single solenoid valve	CPVSC1-M1HT-M-T-Q3	548 043
	5/2-way double solenoid valve	CPVSC1-M1HT-J-T-Q3	548 044
	3/2-way valve, normally open	CPVSC1-M1HT-N-T-Q30	548 042
	3/2-way valve, normally closed	CPVSC1-M1HT-K-T-Q3C	548 041
	2/2-way valve, normally closed	CPVSC1-M1HT-D-T-Q3C	548 040
	Solenoid valve with QS-4 push-in connectors		
	5/2-way single solenoid valve	CPVSC1-M1HT-M-T-Q4	548 048
	5/2-way double solenoid valve	CPVSC1-M1HT-J-T-Q4	548 049
	3/2-way valve, normally open	CPVSC1-M1HT-N-T-Q40	548 047
	3/2-way valve, normally closed	CPVSC1-M1HT-K-T-Q4C	548 046
	2/2-way valve, normally closed	CPVSC1-M1HT-D-T-Q4C	548 045


Ordering data – Valves with individual electrical connection, pushing manual override, horizontal plug, 24 V DC			
Designation		Type	Part No.
	Solenoid valve with M5 connections		
	5/2-way single solenoid valve	CPVSC1-M1HT-M-H-M5	548 053
	5/2-way double solenoid valve	CPVSC1-M1HT-J-H-M5	548 054
	3/2-way valve, normally open	CPVSC1-M1HT-N-H-M50	548 052
	3/2-way valve, normally closed	CPVSC1-M1HT-K-H-M5C	548 051
	2/2-way valve, normally closed	CPVSC1-M1HT-D-H-M5C	548 050
	Solenoid valve with QS-3 push-in connectors		
	5/2-way single solenoid valve	CPVSC1-M1HT-M-H-Q3	548 058
	5/2-way double solenoid valve	CPVSC1-M1HT-J-H-Q3	548 059
	3/2-way valve, normally open	CPVSC1-M1HT-N-H-Q30	548 057
	3/2-way valve, normally closed	CPVSC1-M1HT-K-H-Q3C	548 056
	2/2-way valve, normally closed	CPVSC1-M1HT-D-H-Q3C	548 055
	Solenoid valve with QS-4 push-in connectors		
	5/2-way single solenoid valve	CPVSC1-M1HT-M-H-Q4	548 063
	5/2-way double solenoid valve	CPVSC1-M1HT-J-H-Q4	548 064
	3/2-way valve, normally open	CPVSC1-M1HT-N-H-Q40	548 062
	3/2-way valve, normally closed	CPVSC1-M1HT-K-H-Q4C	548 061
	2/2-way valve, normally closed	CPVSC1-M1HT-D-H-Q4C	548 060

## Valve terminals type 80 CPV-SC, Smart Cubic

Accessories

**FESTO**

Ordering data – Valves with individual electrical connection, detenting manual override, vertical plug, 12 V DC			
Designation		Type	Part No.
	Solenoid valve with M5 connections		
	5/2-way single solenoid valve	CPVSC1-M5H-M-T-M5	547 367
	5/2-way double solenoid valve	CPVSC1-M5H-J-T-M5	547 368
	3/2-way valve, normally open	CPVSC1-M5H-N-T-M50	547 366
	3/2-way valve, normally closed	CPVSC1-M5H-K-T-M5C	547 365
	2/2-way valve, normally closed	CPVSC1-M5H-D-T-M5C	547 364
	Solenoid valve with QS-3 push-in connectors		
	5/2-way single solenoid valve	CPVSC1-M5H-M-T-Q3	547 372
	5/2-way double solenoid valve	CPVSC1-M5H-J-T-Q3	547 373
	3/2-way valve, normally open	CPVSC1-M5H-N-T-Q30	547 371
	3/2-way valve, normally closed	CPVSC1-M5H-K-T-Q3C	547 370
	2/2-way valve, normally closed	CPVSC1-M5H-D-T-Q3C	547 369
	Solenoid valve with QS-4 push-in connectors		
	5/2-way single solenoid valve	CPVSC1-M5H-M-T-Q4	547 377
	5/2-way double solenoid valve	CPVSC1-M5H-J-T-Q4	547 378
	3/2-way valve, normally open	CPVSC1-M5H-N-T-Q40	547 376
3/2-way valve, normally closed	CPVSC1-M5H-K-T-Q4C	547 375	
2/2-way valve, normally closed	CPVSC1-M5H-D-T-Q4C	547 374	


Ordering data – Valves with individual electrical connection, pushing manual override, horizontal plug, 12 V DC			
Designation		Type	Part No.
	Solenoid valve with M5 connections		
	5/2-way single solenoid valve	CPVSC1-M5H-M-H-M5	547 382
	5/2-way double solenoid valve	CPVSC1-M5H-J-H-M5	547 383
	3/2-way valve, normally open	CPVSC1-M5H-N-H-M50	547 381
	3/2-way valve, normally closed	CPVSC1-M5H-K-H-M5C	547 380
	2/2-way valve, normally closed	CPVSC1-M5H-D-H-M5C	547 379
	Solenoid valve with QS-3 push-in connectors		
	5/2-way single solenoid valve	CPVSC1-M5H-M-H-Q3	547 387
	5/2-way double solenoid valve	CPVSC1-M5H-J-H-Q3	547 388
	3/2-way valve, normally open	CPVSC1-M5H-N-H-Q30	547 386
	3/2-way valve, normally closed	CPVSC1-M5H-K-H-Q3C	547 385
	2/2-way valve, normally closed	CPVSC1-M5H-D-H-Q3C	547 384
	Solenoid valve with QS-4 push-in connectors		
	5/2-way single solenoid valve	CPVSC1-M5H-M-H-Q4	547 392
	5/2-way double solenoid valve	CPVSC1-M5H-J-H-Q4	547 393
	3/2-way valve, normally open	CPVSC1-M5H-N-H-Q40	547 391
	3/2-way valve, normally closed	CPVSC1-M5H-K-H-Q4C	547 390
	2/2-way valve, normally closed	CPVSC1-M5H-D-H-Q4C	547 389

# Valve terminals type 80 CPV-SC, Smart Cubic


Accessories

**FESTO**

## Ordering data – Valves with individual electrical connection, detenting manual override, vertical plug, 5 V DC

Designation	Type	Part No.
	Solenoid valve with M5 connections	
	5/2-way single solenoid valve	CPVSC1-M4H-M-T-M5
	5/2-way double solenoid valve	CPVSC1-M4H-J-T-M5
	3/2-way valve, normally open	CPVSC1-M4H-N-T-M5O
	3/2-way valve, normally closed	CPVSC1-M4H-K-T-M5C
	2/2-way valve, normally closed	CPVSC1-M4H-D-T-M5C
	Solenoid valve with QS-3 push-in connectors	
	5/2-way single solenoid valve	CPVSC1-M4H-M-T-Q3
	5/2-way double solenoid valve	CPVSC1-M4H-J-T-Q3
	3/2-way valve, normally open	CPVSC1-M4H-N-T-Q3O
	3/2-way valve, normally closed	CPVSC1-M4H-K-T-Q3C
	2/2-way valve, normally closed	CPVSC1-M4H-D-T-Q3C
	Solenoid valve with QS-4 push-in connectors	
	5/2-way single solenoid valve	CPVSC1-M4H-M-T-Q4
	5/2-way double solenoid valve	CPVSC1-M4H-J-T-Q4
	3/2-way valve, normally open	CPVSC1-M4H-N-T-Q4O
	3/2-way valve, normally closed	CPVSC1-M4H-K-T-Q4C
	2/2-way valve, normally closed	CPVSC1-M4H-D-T-Q4C






## Ordering data – Valves with individual electrical connection, pushing manual override, horizontal plug, 5 V DC

Designation	Type	Part No.
	Solenoid valve with M5 connections	
	5/2-way single solenoid valve	CPVSC1-M4H-M-H-M5
	5/2-way double solenoid valve	CPVSC1-M4H-J-H-M5
	3/2-way valve, normally open	CPVSC1-M4H-N-H-M5O
	3/2-way valve, normally closed	CPVSC1-M4H-K-H-M5C
	2/2-way valve, normally closed	CPVSC1-M4H-D-H-M5C
	Solenoid valve with QS-3 push-in connectors	
	5/2-way single solenoid valve	CPVSC1-M4H-M-H-Q3
	5/2-way double solenoid valve	CPVSC1-M4H-J-H-Q3
	3/2-way valve, normally open	CPVSC1-M4H-N-H-Q3O
	3/2-way valve, normally closed	CPVSC1-M4H-K-H-Q3C
	2/2-way valve, normally closed	CPVSC1-M4H-D-H-Q3C
	Solenoid valve with QS-4 push-in connectors	
	5/2-way single solenoid valve	CPVSC1-M4H-M-H-Q4
	5/2-way double solenoid valve	CPVSC1-M4H-J-H-Q4
	3/2-way valve, normally open	CPVSC1-M4H-N-H-Q4O
	3/2-way valve, normally closed	CPVSC1-M4H-K-H-Q4C
	2/2-way valve, normally closed	CPVSC1-M4H-D-H-Q4C

## Valve terminals type 80 CPV-SC, Smart Cubic

Accessories

**FESTO**





Ordering data – End plates			
Designation		Type	Part No.
Left-hand end plates			
	With external pilot air supply	CPVSC1-EPL-E	527 585
	With internal pilot air supply	CPVSC1-EPL-I	527 583
Right-hand end plates			
	With ducted exhaust air	CPVSC1-EPR-G	527 587
	With unducted exhaust air and flat plate silencer	CPVSC1-EPR-U	527 589
	With unducted exhaust air and round silencer	CPVSC1-EPR-UC	536 060



# Valve terminals type 80 CPV-SC, Smart Cubic

Accessories









**FESTO**

Ordering data – Accessories				
Designation			Type	Part No.
CPI interface				
	Electrical connection		CPVSC1-AE16-CPI	541 975
Control unit				
	Fieldbus Direct – DeviceNet		CPVSC1-AE16-DN	538 654
	Fieldbus Direct – Profibus DP		CPVSC1-AE16-DP	541 919
Individual electrical connection				
	Plug socket with cable, IP40	0.5 m	KMH-0,5	197 263
		1 m	KMH-1	197 264
		2.5 m	KMH-2,5	527 400
		5 m	KMH-5	527 401

# Valve terminals type 80 CPV-SC, Smart Cubic

Accessories






**FESTO**

Ordering data – Accessories				
Designation			Type	Part No.
Power supply				
	Micro Style M12, 5-pin socket (B-coded) for DeviceNet	for 0.75 mm <sup>2</sup>	NTSD-GD-9-M12-5POL-RK	538 999
	M12, 5-pin socket (A-coded) for Profibus DP	for 0.75 mm <sup>2</sup>	FBSD-GD-9-5POL	18 324
Fieldbus connection				
	Fieldbus socket for Micro Style connection, M12, 5-pin socket (A-coded)		FBSD-GD-9-5POL	18 324
	Straight plug, 5-pin, screw terminal		FBS-M12-5GS-PG9	175 380
	T-adapter, 5-pin, for DH-485/DeviceNet		FB-TA-M12-5POL	171 175
Connecting cable, IP40, for multi-pin plug connection				
	Sub-D, 15-pin, up to 12 valve positions for code MS Material: PVC Suitable for chain link trunking	2.5 m	KMP6-15P-12-2,5	527 543
		5 m	KMP6-15P-12-5	527 544
		10 m	KMP6-15P-12-10	527 545
	Sub-D, 26-pin, up to 16 valve positions for code MH Material: PVC Suitable for chain link trunking	2.5 m	KMP6-26P-16-2,5	527 546
		5 m	KMP6-26P-16-5	527 547
		10 m	KMP6-26P-16-10	527 548
Valve terminal connection				
	Angled plug-angled socket	0.25 m	KVI-CP-3-WS-WD-0,25	540 327
	Angled plug-angled socket	0.5 m	KVI-CP-3-WS-WD-0,5	540 328
	Angled plug-angled socket	2 m	KVI-CP-3-WS-WD-2	540 329
	Angled plug-angled socket	5 m	KVI-CP-3-WS-WD-5	540 330
	Angled plug-angled socket	8 m	KVI-CP-3-WS-WD-8	540 331
	GS-GD, straight plug-straight socket	2 m	KVI-CP-3-GS-GD-2	540 332
	Straight plug-straight socket	5 m	KVI-CP-3-GS-GD-5	540 333
	Straight plug-straight socket	8 m	KVI-CP-3-GS-GD-8	540 334

# Valve terminals type 80 CPV-SC, Smart Cubic

Accessories



**FESTO**

Ordering data – Accessories				
Designation			Type	Part No.
Inscription labels for valve identification				
	80 pieces, 9x4.5 mm		MH-BZ-80x	197 259
Inscription label holder				
	1 piece	for 2 valve positions	CPVSC1-ST-2	547 395
		for 3 valve positions	CPVSC1-ST-3	547 396
		for 4 valve positions	CPVSC1-ST-4	527 631
		for 5 valve positions	CPVSC1-ST-5	547 397
		for 6 valve positions	CPVSC1-ST-6	547 398
		for 7 valve positions	CPVSC1-ST-7	547 399
		for 8 valve positions	CPVSC1-ST-8	527 633
		for 9 valve positions	CPVSC1-ST-9	547 400
		for 10 valve positions	CPVSC1-ST-10	547 401
		for 11 valve positions	CPVSC1-ST-11	547 402
		for 12 valve positions	CPVSC1-ST-12	527 635
		for 13 valve positions	CPVSC1-ST-13	547 403
		for 14 valve positions	CPVSC1-ST-14	547 404
		for 15 valve positions	CPVSC1-ST-15	547 405
		for 16 valve positions	CPVSC1-ST-16	527 637
		Tie rod		
	1 piece	for 2 valve positions	CPVSC1-ZA-2	547 416
		for 3 valve positions	CPVSC1-ZA-3	547 417
		for 4 valve positions	CPVSC1-ZA-4	532 807
		for 5 valve positions	CPVSC1-ZA-5	547 418
		for 6 valve positions	CPVSC1-ZA-6	547 419
		for 7 valve positions	CPVSC1-ZA-7	547 420
		for 8 valve positions	CPVSC1-ZA-8	532 808
		for 9 valve positions	CPVSC1-ZA-9	547 421
		for 10 valve positions	CPVSC1-ZA-10	547 422
		for 11 valve positions	CPVSC1-ZA-11	547 423
		for 12 valve positions	CPVSC1-ZA-12	532 809
		for 13 valve positions	CPVSC1-ZA-13	547 424
		for 14 valve positions	CPVSC1-ZA-14	547 425
		for 15 valve positions	CPVSC1-ZA-15	547 426
		for 16 valve positions	CPVSC1-ZA-16	532 810
		Mounting		
	Screw for additional terminal mounting		M3x45	527 643
	Mounting		CPVSC-HS35	527 639

## Valve terminals type 80 CPV-SC, Smart Cubic

Accessories

**FESTO**

Ordering data – Accessories				
Designation			Type	Part No.
User documentation				
	User documentation – Pneumatics, valve terminal CPV-SC	German	P.BE-CPVSC-DE	530 925
		English	P.BE-CPVSC-EN	530 926
		French	P.BE-CPVSC-FR	530 927
		Spanish	P.BE-CPVSC-ES	530 928
		Italian	P.BE-CPVSC-IT	530 929
		Swedish	P.BE-CPVSC-SV	530 930
	User documentation – DeviceNet fieldbus	German	P.BE-CPASC-CPVSC-DN-DE	539 008
		English	P.BE-CPASC-CPVSC-DN-EN	539 009
		French	P.BE-CPASC-CPVSC-DN-FR	539 010
		Spanish	P.BE-CPASC-CPVSC-DN-ES	539 011
		Italian	P.BE-CPASC-CPVSC-DN-IT	539 012
		Swedish	P.BE-CPASC-CPVSC-DN-SV	539 013
	User documentation – Profibus DP fieldbus	German	P.BE-CPASC-CPVSC-DP-DE	548 725
		English	P.BE-CPASC-CPVSC-DP-EN	548 726
		French	P.BE-CPASC-CPVSC-DP-FR	548 728
		Spanish	P.BE-CPASC-CPVSC-DP-ES	548 727
		Italian	P.BE-CPASC-CPVSC-DP-IT	548 729
		Swedish	P.BE-CPASC-CPVSC-DP-SV	548 730