



■ Wide variety of mounting options

■ Infinitely adjustable swivel angle

■ Comprehensive range of accessories


Specified types in accordance with ATEX directive for potentially explosive atmospheres

➔ www.festo.com/en/ex

Semi-rotary drives DSR/DSRL

Features

FESTO



Brief description

In these semi-rotary drives, the force is directly transmitted to the drive shaft via a rotary vane. The swivel angle is infinitely adjustable from 0 ... 184° (DSRL-10 and 12: 0 ... 181°).

The adjustable stop system is separate from the rotary vane so that any forces which occur are absorbed by the stop blocks. The impacts are cushioned at the end positions by flexible plastic plates.

DSRL-...-FW

This design with hollow flanged shaft permits the passage of liquid or gaseous media, or even tubing or

wiring. The force is transmitted directly and backlash-free via a splined shaft.

-  - Note
Sizing software
Calculating inertia
→ www.festo.com

Semi-rotary drives DSR/DSRL


FESTO

Features

Mounting options

Without mounting attachments

Direct mounting



With mounting attachments

for DSR

Foot mounting HSR-...-FW



Flange mounting FSR



Push-on flange FWSR



for DSRL

Foot mounting HSR-...-FW



Freewheel unit for synchronous movements

The freewheel unit is an attachment which is fitted to the drive shaft of the semi-rotary drive DSR. The freewheel unit converts the oscillating rotary movement of the semi-rotary drive into a synchronous, indexing movement. The movement of the semi-rotary drive shaft only occurs in the working directions left or right. This permits infinitely adjustable feed movements.

The minimum possible swivel angle is 0.4°. Switching accuracy is also dependent upon switching speed and load.

- - Note


The load must be stopped externally!

FLSR-...-L (left-hand)
Viewed from the drive shaft side,
rotation counter-clockwise.

FLSR-...-R (right-hand)
Viewed from the drive shaft side,
rotation clockwise.

Accessories
Speed regulation


→ 20




FLSR with semi-rotary drive

Sample applications with hollow flanged shaft in DSRL


Air blast




Vacuum



Electrical lines




Water, coolant, oil, glue, etc.



Semi-rotary drives DSR/DSRL

Peripherals overview and type codes

FESTO



Semi-rotary drives DSR/DSRL

Peripherals overview and type codes

Mounting attachments and accessories				
	Brief description	DSR	DSRL	→ Page/Internet
1	Foot mounting HSR-...-FW	■	■	12
2	Freewheel unit FLSR-...-L/R	■	–	14
3	Flange mounting FSR	■	–	12
4	Push-on flange FWSR	■	–	13
5	Mounting kit WSR-...	■	■	17
6	Mounting kit WSR-12 ... 40	■	■	16
7	Mounting kit WSR-10/12-K	■	■	16
8	Micro switch S-3-BE-SW	■	■	19
9	Micro switch S-3-BE	■	■	19
10	Micro switch SR-3-E-SW	■	■	19
11	Micro switch S-3-E	■	■	19
12	Micro stem actuated valve SO-3-PK-3-B, S-3-PK-3-B	■	■	20
13	Proximity sensors SIEN	■	■	20
14	Push-in L-fitting QSL	■	■	quick star
15	One-way flow control valve GRLA	■	■	20


DSRL		–	10	–	180	–	P	–	FW
Type									
Double-acting									
DSR	Semi-rotary drive with spigot shaft								
DSRL	Semi-rotary drive, with flanged, hollow drive shaft								
Piston Ø [mm]									
Swivel angle [°]									
Cushioning									
P	Non-adjustable at either end								
Shaft									
	Spigot shaft								
FW	Drive shaft								

Semi-rotary drives DSR/DSRL

FESTO

Technical data

Function



Ø - Diameter
10 ... 40 mm

≡ - Force
0.5 ... 20 Nm

www.festo.com

Variants

- With spigot shaft
- With hollow flanged shaft



General technical data						
Piston Ø	10	12	16	25	32	40
Pneumatic connection	M3	M5	M5	M5	G $\frac{1}{8}$	G $\frac{1}{4}$
Design	Semi-rotary actuator with vane drive					
Cushioning	Non-adjustable at either end					
Position sensing	Electrical					
	Pneumatic					
	Inductive					
Type of mounting	Via through-holes					
	Via accessories					
Mounting position	Any					
Max. swivel angle	0 ... 181 °		0 ... 184 °			

Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Operating and environmental conditions						
Piston Ø	10	12	16	25	32	40
Operating medium	Filtered compressed air, lubricated or unlubricated					
Operating pressure	[bar]	2.5 ... 8		2 ... 8		1.5 ... 8
Temperature range ¹⁾	[°C]	-10 ... +60				

¹⁾ Note operating range of proximity sensors

Forces and torques						
Piston Ø	10	12	16	25	32	40
Torque at 6 bar [Nm]	0.5	1	2	5	10	20
Max. swivelling frequency ¹⁾ [Hz]	3					
Max. perm. radial load ²⁾ [N]	30	45	75	120	200	350
Max. perm. axial load ²⁾ [N]	10	18	30	50	75	120
Max. perm. mass moment of inertia ²⁾	Diagrams → 8					

¹⁾ Please observe the max. permissible mass moments of inertia → 8

²⁾ On the drive shaft at maximum frequency


Semi-rotary drives DSR/DSRL

Technical data

FESTO

Materials

Sectional view



Rotary actuator		
1	Housing	Die-cast zinc
2	Drive shaft	Nickel plated steel
3	Rotary vane	Plastic
4	Trip cam	Sintered steel, nickel plated
5	Cover cap	Plastic
–	Seals	Nitrile rubber

Weights [g]						
Piston Ø	10	12	16	25	32	40
DSR-...-P	100	200	310	540	1,285	2,400
DSRL-...-FW	140	240	350	610	1,390	2,700

Semi-rotary drives DSR/DSRL


Technical data

FESTO


Max. permissible mass moment of inertia

Mass moment of inertia m as a function of swivel time S and swivel angle


DSR/DSRL-10




DSR/DSRL-12




DSR/DSRL-16




DSR/DSRL-25



DSR/DSRL-32



DSR/DSRL-40



Note

Sizing software
Calculating inertia
→ www.festo.com


----- Swivel angle 90°
..... Swivel angle 120°
———— Swivel angle 180°

Assembly instructions:


If the listed maximum permissible mass moment of inertia is exceeded, external stops must be attached. Please note:

The stop must not be less than the minimum radius to the drive shaft (r_{min}). The stop force must not exceed

the maximum force. Due to the flexibility of the stops, a precise end position can only be achieved using external stops.



Ø [mm]	Stop radius r_{min} [mm]	Force [N]
10	13	60
12	15	90
16	17	160
25	21	320
32	28	480
40	40	650



Note

When throttling the semi-rotary drives to swivelling speeds under 180°/s, the drives must be operated

at a pressure of at least 6 bar. A constant speed fluctuation of $\pm 30\%$ is to be expected. The flutters and

swivelling times shown in the diagrams can only be improved by using flow control valves.

Semi-rotary drives DSR/DSRL


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

DSR



Note

The swivel angle is 180° and pressure-dependent. The cushioning angle on each side is approx. 1.6° maximum at 8 bar.

If after the swivel process, the kinetic energy is converted by cushioning, the drive shaft swivels back by a corresponding angle.

The stops must not be removed as the rotary vane is not suitable for end-position limiting. The cover cap is equipped with an angle scale for adjusting.

When attaching additional components to the drive shaft, the maximum permissible tightening torque of the bolt at D4 must not be exceeded.

1 Angle scale for swivel angle reading

2 Woodruff key position at 0°

3 Supply port

∅	B1	B2	B3	D1 ∅ g7	D2 ∅	D3 ∅ h8	D4	E1	E2	H1	H2	H3	L1	L2
[mm]														
10	22	32	53	6	12	20	M2.5	M3	M3	19.4	15.5	38.8	57	22.4
12	26	40	65	8	16	22	M3	M5	M3	23.5	18.5	48	65.6	25.5
16	30	46	78	10	17	24	M3	M5	M3	27	20.5	56.5	75.8	29
25	42	60	98	12	18	28	M4	M5	M4	30	23	68.1	94.5	35.4
32	54	80	130	16	27	42	M5	G $\frac{1}{8}$	M4	43	34	92	125.5	50
40	70	100	160	20	36	52	M6	G $\frac{1}{4}$	M4	53	40	121	162	60

∅	L3	L4	L5	L6	L7	S1	S2	T1	T2	X	Woodruff key to DIN 6885 ¹⁾	Tightening torque at D4 [Nm]
[mm]												
10	6.5	4.5	15.1	2.2	2	3.4	6	6.8	7	0.35	A2 x 2 x 12	0.7
12	5.5	3.5	18	2.1	2.5	4.4	8	8.8	9	0.35	A2 x 2 x 16	1.2
16	6	3.5	22.5	2.1	–	5.5	10	11.2	9	0.35	A3 x 3 x 18	1.2
25	5.4	3	30	4	–	7	11	13.5	10	0.4	A4 x 4 x 25	5.5
32	10	7	36	4	–	8.5	15	18	12.5	0.45	A5 x 5 x 36	5.5
40	10	6	50	4	–	8.5	15	22.5	16	0.5	A6 x 6 x 45	5.5

1) included in scope of delivery

– Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Semi-rotary drives DSR/DSRL


Technical data

FESTO

Dimensions

DSRL

Download CAD data → www.festo.com



1 Angle scale for swivel angle reading

2 Position of marking at angle scale 0°

3 Supply port

4 Through-hole

Note

The swivel angle is 180° and pressure-dependent. The cushioning angle on each side is approx. 1.6° maximum at 8 bar.

If after the swivel process, the kinetic energy is converted by cushioning, the drive shaft swivels back by a corresponding angle.

The stops must not be removed as the rotary vane is not suitable for end-position limiting. The cover cap is equipped with an angle scale for adjusting.

When attaching additional components to the drive flange, the maximum permissible tightening torque of the bolt at D4 must not be exceeded.

Ø	B1	B2	B3	D1 Ø g7	D2 Ø	D3 Ø h8	D4	D5 Ø f8	D6 Ø	D7 Ø H13	D8 Ø min.	E1	E2	E3	H1
[mm]															
10	22	32	53	30	10	20	M3	11	21	3.4	1.5	M3	M3	M3	19.4
12	26	40	65	33	13	22	M3	14	25	3.4	1.5	M5	M3	M3	23.5
16	30	46	78	38	14	24	M5	16	28	4.5	3.5	M5	M3	M4	27
25	42	60	98	46	17	28	M5	20	35	5.5	3.5	M5	M4	M5	30
32	54	80	130	60	24	42	G½	28	45	6.5	7	G½	M4	M6	43
40	70	100	160	70	30	52	G½	36	54	9	7	G¾	M4	M8	53

Ø	H2	H3	L1	L2	L3	L4	L5	L6	L7	L8	S1	S2	T1	X	Tightening torque at D4 [Nm]
[mm]															
10	15.5	38.8	49	14	12.3	4.5	15.1	3	2.2	2	3.4	6	5	0.35	0.7
12	18.5	48	54.2	13.5	11.5	3.5	18	3	2.1	2.5	4.4	8	5	0.35	1.2
16	20.5	56.5	64.7	16	14	3.5	22.5	4	2.1	–	5.5	10	6	0.35	1.2
25	23	68.1	78	18.5	15.5	3	30	4.5	4	–	7	11	6	0.4	5.5
32	34	92	102.8	26	22	7	36	6	4	–	8.5	15	8	0.45	5.5
40	40	121	134.5	31	26	6	50	7.5	4	–	8.5	15	8	0.5	5.5

– Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Semi-rotary drives DSR/DSRL

Technical data

FESTO

Ordering data				
Rotary actuator	Design	Ø [mm]	Part No.	Type
DSR-...-P				
	With spigot shaft	10	33 297	DSR-10-180-P
		12	11 909	DSR-12-180-P
		16	11 910	DSR-16-180-P
		25	11 911	DSR-25-180-P
		32	11 912	DSR-32-180-P
		40	13 467	DSR-40-180-P
DSRL-...-P-FW				
	With hollow flanged shaft	10	33 296	DSRL-10-180-P-FW
		12	30 654	DSRL-12-180-P-FW
		16	30 655	DSRL-16-180-P-FW
		25	30 656	DSRL-25-180-P-FW
		32	30 657	DSRL-32-180-P-FW
		40	30 658	DSRL-40-180-P-FW

Semi-rotary drives DSR/DSRL


Accessories

FESTO

Foot mounting HSR-...-FW

Material:

Steel



Dimensions and ordering data															
For Ø	B1	B2	D1 Ø H13	D2	D10	H1	H2	L1	L2	L3	N1	CRC ¹⁾	Weight	Part No.	Type
[mm]													[g]		
10	53.5	43	3.5	2	20	4	53	11	17	21	34	2	61	33 317	HSR-10-FW
12	64	52	3.5	2	22	4	63	11	17	21	40	2	87	30 923	HSR-12-FW
16	77	63	5.7	2	24	5	71	14	22	26.5	44	2	170	30 924	HSR-16-FW
25	97	80	6.8	3	28	5	76	16	28	34	47	2	235	30 925	HSR-25-FW
32	129	105	8.8	4	42	8	108	20	34	43	66	2	660	30 926	HSR-32-FW
40	159	130	8.8	5	52	8	134	25	42	52	81	2	1,040	30 927	HSR-40-FW


1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents

Flange mounting FSR

Material:

Aluminium



Dimensions and ordering data														
For Ø	B3	B4	D3 Ø min.	D4	D5 Ø H13	D6 Ø H13	H3	L4	N2	R	CRC ¹⁾	Weight	Part No.	Type
[mm]								max.				[g]		
10	28	46	13	M3	3.4	6.5	7	2	20	18	2	22	34 480	FSR-10
12	31	54	17	M3	3.4	6.5	7	2	22	20.5	2	32	14 658	FSR-12
16	35	62	19	M4	4.5	8.5	8	2	26.5	23.5	2	50	13 236	FSR-16
25	40	76	21	M5	5.5	10.4	8	2.5	29	27	2	70	13 237	FSR-25
32	56	100	32	M6	6.6	12.4	12	2.5	42	36	2	180	13 238	FSR-32
40	72	120	37	M8	9	16.4	14	4	52	46	2	300	14 655	FSR-40

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents

Semi-rotary drives DSR/DSRL

Accessories


FESTO

Push-on flange FWSR

The permissible tightening torque may not be exceeded when installing the push-on flange FWSR on the drive shaft.

Material:

Wrought aluminium alloy, anodised
Copper, PTFE and silicone free



Dimensions and ordering data													
For Ø	B5	D4	D5 Ø H13	D7 Ø f8	D8	D9	L5	L6	L7	Tightening torque [Nm]	CRC ¹⁾	Weight [g]	Part No. Type
[mm]													
10	21	M3	3.4	11	30	12	22	3	1.6	0.7	2	10	32 798 FWSR-10
12	25	M3	3.4	14	35	15	25	3	3	1.2	2	19	14 659 FWSR-12
16	28	M4	4.5	16	40	17	28	5	3	1.2	2	30	13 239 FWSR-16
25	35	M5	5.5	20	50	23	38	8	3	5.5	2	70	13 240 FWSR-25
32	45	M6	6.6	28	60	28	48	10	4	5.5	2	120	13 241 FWSR-32
40	54	M8	9	36	70	38	60	11	5	5.5	2	240	14 656 FWSR-40

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents

Semi-rotary drives DSR/DSRL

Accessories

FESTO


Freewheel unit FLSR

Material:

Housing: Aluminium die-cast

Sleeve, shaft: Case-hardened steel

Seal, cap: Nitrile rubber




General technical data						
Piston Ø	10	12	16	25	32	40
Design	Freewheel unit as attachment					
Rotation angle	Infinitely adjustable steps (independent of rotation angle)					
Applied radial load [N]	52	77	160	350	200	350
Applied axial load [N]	30	50	100	200	75	120
Max. torque [Nm]	0.7	1.3	2.7	6.6	13.3	26.7
Frequency	3 Hz ($\frac{1}{3}$ · The load must be stopped externally!)					
Temperature range [°C]	-10 ... +60					

Direction of rotation


The freewheel unit blocks one of the two possible swivel directions of the DSM swivel module.

FLSM-...-R, right-hand (clockwise) rotation



1 Viewed towards drive shaft

FLSM-...-L, left-hand (counter-clockwise) rotation



Semi-rotary drives DSR/DSRL

Accessories

FESTO

Dimensions and ordering data															
For Ø [mm]	B4	B5	B6	D1 Ø g7	D3 Ø h8	D4	D5 Ø H13	D6	H4	H5	L6	L7	L8	L9	L10
10	38	45	38.5	6	20	–	3.3	M3	20	42.5	3.5	4.2	41.5	20.2	23
12	42	49	41.5	8	25	M3	3.3	M3	24	48.5	3.5	4.5	47.3	24.5	25
16	50	60	50	10	24	M3	4.5	M4	28	58	3.5	4.4	47	27.4	23.5
25	60	75	60	12	28	M4	6.6	M6	31	68.5	3.5	4.1	48	34	24
32	83	98	83	16	42	M5	6.6	M6	44	93	7.2	8.5	60	48.5	30
40	96	114	96	20	52	M6	8.6	M8	54	111	6	8	75	58	38

For Ø [mm]	T1	T2	T3	T4	T5	Woodruff key ¹⁾ to DIN 6885	CRC ²⁾	Weight [g]	Direction of rotation	Part No.	Type
10	6.8	8	8	5	8	A2 x 2 x 12	2	165	left-hand	33 298	FLSR-10-L
									right-hand	33 299	FLSR-10-R
12	8.8	9	8	5	9	A2 x 2 x 16	2	225	left-hand	30 930	FLSR-12-L
									right-hand	30 929	FLSR-12-R
16	11.2	11	10	8	11	A3 x 3 x 18	2	340	left-hand	15 281	FLSR-16-L
									right-hand	15 280	FLSR-16-R
25	13.5	14	12	11	14	A4 x 4 x 25	2	500	left-hand	13 778	FLSR-25-L
									right-hand	13 730	FLSR-25-R
32	18	16	12	11	16	A5 x 5 x 36	2	1 140	left-hand	15 688	FLSR-32-L
									right-hand	15 687	FLSR-32-R
40	22.5	21	15	11	21	A6 x 6 x 45	2	1 800	left-hand	19 037	FLSR-40-L
									right-hand	19 036	FLSR-40-R

1) included in scope of delivery

2) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents

Semi-rotary drives DSR/DSRL

Accessories

FESTO


Mounting kit

WSR-10/12-K

for micro switch S-3-BE, S-3-BE-SW

Material:

Steel



Dimensions and ordering data									
For Ø	B	H1	H2	L3	CRC ¹⁾	Weight	Part No.	Type	
[mm]						[g]			
10	15	1	22.2	47	2	11	33 414	WSR-10-K	
12	15	1	25.1	53	2	13	15 686	WSR-12-K	

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents

Mounting kit

WSR-12 ... 40



for micro switch S-3-E, SR-3-E-SW and

micro stem actuated valve

S-3-PK-3-B, SO-3-PK-3-B

Material:

Steel



Dimensions and ordering data										
For Ø	B1	B2	B3	H1	H2	L2	L3	CRC ¹⁾	Weight	Part No. Type
[mm]									[g]	
12	5.8	23.4	4	1.5	23	14	79	2	12	15 684 WSR-12
16	10	26.5	4.5	1.5	29.8	19	84.5	2	23	14 874 WSR-16
25	12	29	2	1.5	38	24.5	90	2	26	14 796 WSR-25
32	12	29	2	1.5	49.2	40.5	107	2	29	14 960 WSR-32
40	12	29	2	1.5	68.7	52	118.5	2	32	14 961 WSR-40

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents

Semi-rotary drives DSR/DSRL

Accessories

FESTO

Mounting kit

WSR-...-J


for proximity sensors SIEN-M8

WSR-...-J-M5

for proximity sensors SIEN-M5

Material:

Steel



Dimensions and ordering data									
WSR-...-J									
For Ø	B4	H3	H4	L4	L5	CRC ¹⁾	Weight	Part No.	Type
[mm]							[g]		
16	13	1.5	35	52	27	2	12	14 873	WSR-16-J
25	13	1.5	43.1	52	34	2	17	14 799	WSR-25-J
32	13	1.5	54.3	64	48	2	18	14 962	WSR-32-J
40	13	1.5	76.3	80	60	2	24	14 963	WSR-40-J

WSR-...-J-M5									
For Ø	B4	H3	H4	L4	L5	CRC ¹⁾	Weight	Part No.	Type
[mm]							[g]		
10	8	1	25.4	30	20	2	6	33 413	WSR-10-J-M5
12	8	1	28.3	34	24.5	2	10	15 685	WSR-12-J-M5
16	8	1	34.9	38	27	2	78	15 931	WSR-16-J-M5
25	13	1.5	43	52	34	2	17	15 932	WSR-25-J-M5
32	13	1.5	54.3	64	48	2	25	15 933	WSR-32-J-M5
40	13	1.5	76.3	80	60	2	30	15 934	WSR-40-J-M5

1) Corrosion resistance class 2 according to Festo standard 940 070


Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents

Semi-rotary drives DSR/DSRL

Accessories

FESTO

Electrical limit switch for end-position sensing



The switching point may only be exceeded by 0.5 mm in these electrical limit switches. Actuation only vertical to stem axis.


	S-3-BE	S-3-BE-SW	S-3-E	SR-3-E-SW
Connection	3 push-in connectors (2.8x0.5 mm)	3 wires (0.75 mm ²)	Screw connector	3 wires 0.5 m long
Contact rating	➔ Table below			
Operating voltage	250 V AC/250 V DC			
Line current ohmic load	–	–	6 A/250 V AC 0.25 A/250 V DC	5 A/250 V AC 0.25 A/250 V DC
Line current inductive load	–	–	2 A/250 V AC 0.1 A/250 V DC	2 A/250 V AC 0.03 A/250 V DC
Utilisation category	AC 12/DC 12 (ohmic load)			
	AC 14/DC 13 (inductive load)			
CE symbol	Yes, as per EU Directive 73/23/EEC			
Protection class to EN 60 529	IP40	IP67	IP 00	IP65
Temperature range	–20 ... +85 °C		–20 ... +80 °C	
Material	Housing, cover: black plastic			
Weight	2 g	16 g	7 g	10 g

Test symbols:


S-3-BE: VDE-ÜG, UL, CSA, SEMKO
S-3-BE-SW: VDE, SEV, SEMKO, BEAB
S-3-E: VDE, ÖVE, SEMKO, SEV, UL, CSA

Contact configuration:


Changeover switch



NC contact





NO contact



S-3-BE, S-3-BE-SW

AC voltage				
Voltage [V] ~	Resistance load [A]		Inductive load [A]	
12	6		6	
24	3		2	
60	1		0.5	
110	0.5		0.2	
220	0.25		0.1	
S-3-E	DC	AC	DC	AC
12	6	–	6	–
24	6	–	6	–
60	1	–	0.5	–
110	0.5	–	0.2	–
220	0.25	–	0.1	–
250	–	6	–	2
SR-3-E-SW	DC	AC	DC	AC
15	3	–	5	–
30	3	–	5	–
50	1	–	1	–
75	0.25	–	0.75	–
125	0.03	5	0.5	5
250	0.03	5	0.25	5

Pneumatic limit valve for end-position sensing



The switching point is pressure-dependent and deviates up to 0.8 mm in the pressure range from 0 ... 8 bar. The switching point may only be exceeded by 0.5 mm. The valve must not be used as a fixed stop and should only be operated vertically to the stem.

S-3-PK-3-B/SO-3-PK-3-B

Connection	Barbed fitting for 3 mm plastic tubing
Nominal size	1.8 mm
Standard nominal flow rate (1 > 2)	60 l/min
Pressure range	–0.95 ... +8 bar
Actuating force at 6 bar	6 N
Temperature range	–10 ... +60 °C
Materials	Plastic, brass
Weight	7 g

Semi-rotary drives DSR/DSRL



Accessories

FESTO

Electrical limit switch for end-position sensing


Micro switch

S-3-BE




Micro switch with cable (splash-proof)

S-3-BE-SW




Micro switch

S-3-E



Micro switch with roller lever
(splash-proof)

SR-3-E-SW



Ordering data

For Ø	Electrical limit switches, splash-proof	Design	Part No.	Type
[mm]				
10 ... 12			30 648	S-3-BE
		With cable	30 649	S-3-BE-SW
16 ... 40		With roller lever	7 347	S-3-E
			14 797	SR-3-E-SW

Semi-rotary drives DSR/DSRL

Accessories



FESTO

Pneumatic limit valve for end-position sensing

Micro stem actuated valve

S-3-PK-3-B

SO-3-PK-3-B



- | | | |
|---|---|--------------------------------|
| 1 | Barbed fittings for 3 mm plastic tubing | 1 (P) = supply port |
| 2 | Switching point min. | 2 (A) = working or outlet line |
| | | 3 (R) = exhaust |

Ordering data				
For Ø	Pneumatic limit switch	Design	Part No.	Type
[mm]				
16 ... 40		Normally closed	7 843	S-3-PK-3-B
		Normally open	10 403	SO-3-PK-3-B

Ordering data – Proximity sensors, inductive				Technical data → Internet: sien	
	For Ø	Remarks	Connection	Part No.	Type
	10 ... 40	For mounting kit WSR-...-J-M5	Cable	150 370	SIEN-M5B-PS-K-L
			Plug	150 371	SIEN-M5B-PS-S-L
	16 ... 40	For mounting kit WRM-...-J	Cable	150 386	SIEN-M8B-PS-K-L
			Plug	150 387	SIEN-M8B-PS-S-L

Ordering data – Connecting cables				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 333	NEBU-M8G3-K-2.5-LE3
			5	541 334	NEBU-M8G3-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 338	NEBU-M8W3-K-2.5-LE3
			5	541 341	NEBU-M8W3-K-5-LE3

Ordering data – One-way flow control valves				Technical data → Internet: grla	
	Connection		Material	Part No.	Type
	Thread	For tubing OD			
	M3	3	Metal design	175 041	GRLA-M3-QS-3
		3		193 137	GRLA-M5-QS-3-D
	M5	4		193 138	GRLA-M5-QS-4-D
		6		193 139	GRLA-M5-QS-6-D
		3		193 142	GRLA-1/8-QS-3-D
		4		193 143	GRLA-1/8-QS-4-D
		6		193 144	GRLA-1/8-QS-6-D
		8		193 145	GRLA-1/8-QS-8-D
	G1/8	6		193 146	GRLA-1/4-QS-6-D
		8		193 147	GRLA-1/4-QS-8-D
		10		193 148	GRLA-1/4-QS-10-D

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

United States

Customer Resource Center

502 Earth City Expy., Suite 125
Earth City, MO 63045

For ordering assistance, or to find
your nearest Festo Distributor,

Call: 1.800.99.FESTO

Fax: 1.800.96.FESTO

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO

Fax: 1.800.96.FESTO

Email: product.support@us.festo.com

Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788
www.festo.com/us

Sales Offices

Appleton

N. 922 Tower View Drive, Suite N
Greenville, WI 54942

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057

Detroit - Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326

New York

395 Moreland Road
Hauppauge, NY 11788

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550

Design and Manufacturing Operations



East: 395 Moreland Road, Hauppauge, NY 11788



Central: 1441 East Business Center Drive, Mt. Prospect, IL 60056



West: 4935 Southfront Road, Suite F, Livermore, CA 94550

Mexico

Headquarters

Festo Pneumatic, S.A.
Av. Ceylán 3, Col. Tequesquahuac
54020 Tlalnepantla, Edo. de México
Call: 011 52 [55] 53 21 66 00
Fax: 011 52 [55] 53 21 66 65
Email: festo.mexico@mx.festo.com
www.festo.com/mx



Canada

Headquarters

Festo Inc.
5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Call: 1.905.624.9000
Fax: 1.905.624.9001
Email: info.ca@ca.festo.com
www.festo.com/ca



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan
Latvia Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com