

Checkbox CHB



Checkbox CHB

Key features

FESTO




Industrial design

- Compact integrated construction, protected against external light and maladjustment, IP54 protection class
- Flexible installation, thanks to a modular system concept



Easy to use

- Automatic Teach-in of new parts in seconds, no programming required
- Robust recognition algorithm based on part characteristics
- Up to 48 different parts can be saved to memory




Sturdy construction and high functionality

- High conveying performance thanks to variable belt speed (standard: 300 mm/s)
- Maintenance-free system
- Sturdy pneumatic components: Integrated valves and flow controls
- Long service life thanks to brushless DC servo motor



High reliability and checking performance

- Simple, sturdy optics with high-quality industrial line-scan camera and LED light strip
- Insensitive to extraneous light, with contour detection via back-lighting method
- High resolution: 0.02 mm or 0.1 mm



Checkbox CHB

Key features

FESTO


The Checkbox family CHB

The Checkbox is a system for the optical orientation detection and quality inspection of small parts. It consists of an optical unit, e.g. a conveying unit with integral camera and a control unit. The part to be inspected is fed past the camera on the conveyor belt. The

control unit analyses the contour of the part and distinguishes between good parts and those which are incorrectly oriented or defective and foreign parts. All Checkbox units feature a Teach-in function which allows them to "learn"

different parts automatically – without the need for programming. They are easy to use – the press of a button is all that is needed to change your feed system over from one part type to another. The Checkbox is used wherever small

parts need to be fed into assembly or machining units. This is where mechanical sorting devices reach their limits, especially where parts of complex shape or fast cycle times are involved. This calls for intelligent optical devices: The Checkbox family.



Identbox CHB-IB



The Identbox is the basic unit in the Checkbox family and is used to separate good parts, incorrectly-oriented parts and defective parts.

Countbox CHB-CB



The Countbox combines the features of the Identbox with a function for counting good parts with pre-selection of the desired quantity.

Sortbox CHB-SB



The Sortbox unites the functions of the Identbox and the Countbox in one unit and also conveys, sorts and compiles several different types of parts.

Checkbox CHB

Key features

FESTO

Which parts are suitable?



Here is a small selection of the many possibilities:

- Axes
- Bolts
- Brushes
- Buttons
- Ceramic seals
- Curtain hangers
- Drill bits
- Drills
- Fuses
- Game pieces
- Glass ampoules
- Inserts
- Insulating terminals
- Lever stoppers
- Link plates
- Lipstick casings
- Lock nuts
- Mouldings
- Mountings
- Needles
- O-rings
- Pen tops
- Plastic housings
- Plug connectors
- Screws
- Self-locking nuts
- Sensor housings
- Shafts
- Sleeves
- Small wares
- Sockets
- Spring washers
- Springs
- Stampings
- Switch contacts
- Tablets
- Threaded pins
- Toothbrush components
- Turned parts
- Wall plugs
- Washers
- Wooden dowels
- Zip-fastener components

Which industries use the Checkbox family?


- Metalworking industry
- Electrical engineering industry
- Woodworking industry
- Electroplating industry
- Injection moulding industry
- Packaging industry
- Pharmaceutical industry
- Cosmetics industry
- Jewellery industry
- Textile and clothing industry
- Assembly-systems industry
- Food industry
- Precision engineering industry

Checkbox CHB

Key features

FESTO

Contour recognition using back-lighting method



What does the camera see?

Part to be checked
Brass sleeve



Camera image
Brass sleeve



Part to be checked
Valve spring



Camera image
Valve spring



Part to be checked
Plug connector



Camera image
Plug connector



Part to be checked
Unmachined rod clevis



Camera image
Unmachined rod clevis



Part to be checked
Link plate




Camera image
Link plate



Part to be checked
Insulating terminal insert



Camera image
Insulating terminal insert



Checkbox CHB

Product range and peripherals overview

FESTO

Possible combinations		
Identbox CHB-IB	Countbox CHB-CB	Sortbox CHB-SB



Technical data → 10




Technical data → 10



Technical data → 10

Connecting cable Control unit/conveying unit

Cable lengths: 2 m
3 m
5 m



Conveying unit	Tunnel version
with reject positions and conveyor belt	without reject positions and conveyor belt


Part Ø 0.5 ... 10 mm
Part length: 3 mm and above



Part Ø 3 ... 30 mm
Part length: 3 mm and above



Part Ø 3 ... 80 mm
Part length: 5 mm and above



Part Ø 3 ... 30 mm
Part length: 3 mm and above



Part Ø 3 ... 80 mm
Part length: 5 mm and above



Checkbox CHB

Selection aid



Product features			
	Identbox CHB-IB	Countbox CHB-CB	Sortbox CHB-SB
Performance characteristics			
Basic unit with full checking functionality	■	■	■
Up to 48 parts can be taught-in	■	■	■
Three feed paths: – Good parts › to the assembly station – Incorrectly oriented parts › back to the bowl feeder – Defective or foreign parts › to the reject bin	■	■	■
Automatic control of the bowl feeder	■	■	■
Monitoring of part buffer zones	■	■	■
Self-diagnosis	■	■	■
Can be remote-controlled	■	■	■
Integrated counting function: – 1 ... 10 million parts can be pre-selected – When desired quantity is reached › signal to downstream machine – Upon acknowledgement › start of next cycle – Continuous counting for production monitoring		■	■
Simultaneous conveying of different part types and sorting into different buffer zones			■
Compiling of several parts			■
Sample applications			
Correctly oriented feeding at high cycle rates	■	■	■
Automatic rejection of defective or foreign parts	■	■	■
Quality inspection of turned and milled components for chips, burrs, etc.	■	■	■
Ejection of end pieces following automatic bar turning	■	■	■
Feeding of predetermined quantities of parts for packaging and compiling functions		■	■
Set feeding of small parts on to assembly pallets		■	■
Triggering of maintenance cycles		■	■
Feeding to several buffer zones from one bowl feeder (space saving)			■
Packaging terminal: Fully-automated control and monitoring of compiling procedures with several parts and different numbers of items			■
Sorting of mixed parts (e.g. after galvanising or grinding)			■


Checkbox CHB

Sample applications


FESTO

Feeding of parts




Vibratory bowl feeder



Centrifugal bowl feeder




Linear conveyor




Transfer of parts


Slide into the processing centre




Chute



Downpipe



Triple buffer zone



Checkbox CHB

Type code

FESTO

		CHB	-	SB	-	F30	-	L4P	-	K20	-	D	-	EC	-	V33	-	VA	-	BTA
Basic function																				
CHB	Checkbox family																			
Control function																				
IB	Identbox																			
CB	Countbox																			
SB	Sortbox																			
Component size																				
F10	for Ø 0.5 ... 10 mm																			
F30	for Ø 3 ... 30 mm																			
F80	for Ø 3 ... 80 mm																			
Transport function																				
L2P	2 reject pos., belt transport dir.: to the left																			
R2P	2 reject pos., belt transport dir.: to the right																			
L4P	4 reject pos., belt transport dir.: to the left																			
R4P	4 reject pos., belt transport dir.: to the right																			
L6P	6 reject pos., belt transport dir.: to the left																			
R6P	6 reject pos., belt transport dir.: to the right																			
TU	without reject positions and conveyor belt																			
Connecting cable																				
K20	2 m long																			
K30	3 m long																			
K50	5 m long																			
User manual																				
D	German																			
E	English																			
F	French																			
S	Spanish																			
I	Italian																			
Additional function																				
EC	Encoder																			
Field of view																				
V10	Adjustment to 10 mm																			
V20	Adjustment to 20 mm																			
V33	Adjustment to 33 mm																			
Guiding bar material																				
VA	Stainless steel																			
Alternative conveyor belts																				
BTA	with longitudinal ridges																			
BTB	with longitudinal recesses																			

Checkbox CHB

Technical data

FESTO

Identbox


CHB-IB

Countbox

CHB-CB

Sortbox

CHB-SB



General technical data			
For part sizes	Ø 10 mm	Ø 30 mm	Ø 80 mm
Min. component Ø	[mm] 0.5	3	3
Max. component Ø	[mm] 10	30	80
Min. component length	[mm] 3	3	5
Max. component length	Dependent on belt speed and required resolution		
Component range	Rotationally symmetrical parts and pre-oriented parts of any shape		
Camera resolution	[mm] 0.02	0.1	
Exposure time	[µs] 72 ... 8 192	136 ... 8 192	
Number of part memories	48		
Max. number of different orientations per memorised part	8		
Orientation	Part orientation function within checking and counting process can be switched off		
Belt speed	[mm/s] 200 (adjustable: 100 ... 250)	300 (adjustable: 100 ... 400)	
Conveyor rate of good parts	Depending on the size of the component, the number and frequency of the supplied and requested component orientations. Example: 4 screws (M3x25) per second, in the correct position for mounting 4 axes (Ø 18 x 5 mm) per second, for quality check		
Only with CHB-CB and CHB-SB			
Quantity pre-selection	CheckOpti software		
Counting range	1 ... 10 million per part type		

Electrical data	
Operating voltage range AC	[V] 85 ... 264 (at 50/60 Hz)
Max. power consumption	[VA] 100
Internal fuse protection	1 A, slow-blowing, safety circuit breaker integrated in mains switch

Operating and environmental conditions	
Ambient temperature	[°C] 10 ... 50
Protection class	IP54
Operating medium	Filtered, unlubricated compressed air, grade of filtration 40 µm
Operating pressure	[bar] 6
Installation site	Dry, screened from extreme external light sources, cleanest possible ambient air

Checkbox CHB

Technical data

FESTO

Interfaces		
PLC coupling outputs		The connection of an external power supply is recommended in order to achieve full electrical isolation. Load per output: < 100 mA, total load < 1 A
		Ready for operation Error output Feeder control Conveyor belt control Part acceptable and correctly oriented Part acceptable but incorrectly oriented Wrong part
	Additionally with CHB-CB CHB-SB	Pre-selected counter reading reached
	CHB-SB	1 ... 6 (recognised type)
PLC coupling inputs		External type select External start Buffer zone sensors External sensor
	Additionally with CHB-CB CHB-SB	Start new counting cycle
Diagnostic interface		RS 232 interface (115 kBaud), socket, M12x1, 4-pin Cable included in scope of delivery

Weights [g]			
For part sizes	Ø 10 mm	Ø 30 mm	Ø 80 mm
Control unit	6 000		
Conveying unit with 2 reject positions	4 000	7 000	12 000

Checkbox CHB




Technical data

FESTO


Dimensions

Download CAD Data → www.festo.com/us/cad

Control unit



Rear view (rotated 180°)



- 1 PLC coupling
- 2 RS 232 diagnostic interface
- 3 Small-parts conveyor control
- 4 Buffer zone sensors
- 5 Cable to conveying unit

Checkbox CHB


Technical data

FESTO


Dimensions – Conveying unit, part sizes up to $\varnothing 10$ mm

Download CAD Data → www.festo.com/us/cad


2 reject positions



4 reject positions



6 reject positions



Checkbox CHB


Technical data

FESTO


Dimensions – Conveying unit, part sizes up to $\varnothing 30$ mm

Download CAD Data → www.festo.com/us/cad


2 reject positions



4 reject positions



6 reject positions



Checkbox CHB


Technical data

FESTO

Dimensions – Conveying unit, part sizes up to $\varnothing 80$ mm

Download CAD Data → www.festo.com/us/cad

2 reject positions



Checkbox CHB


Technical data

FESTO

Dimensions – Tunnel variant, for part sizes up to $\varnothing 30$ mm

Download CAD Data → www.festo.com/us/cad

Without reject positions and conveyor belt




- 1 2x connecting thread M8 for 50x50 mm profile support
- 2 Part sizes $\varnothing 3 \dots \varnothing 30$ mm
- 3 Conveyor belt
- 4 Guiding bar
- 5 Provide cutout for camera light beam (approx. 5°)

Dimensions – Tunnel variant, for part sizes up to $\varnothing 80$ mm

Download CAD Data → www.festo.com/us/cad

Without reject positions and conveyor belt



- 1 2x connecting thread M8 for 50x50 mm profile support
- 2 Part sizes $\varnothing 3 \dots \varnothing 80$ mm
- 3 Conveyor belt
- 4 Guiding bar

Checkbox CHB


Accessories

FESTO

Dimensions – Mounting options


Download CAD Data → www.festo.com/us/cad

50x50 mm profile support



- 1 50x50 mm profile support
- 2 Profile connector HV-50 as adapter

80x80 mm profile support



- 1 80x80 mm profile support
- 2 Automatic profile connector
- 3 4 socket head screws M6x40 DIN 912

Checkbox CHB

Ordering data – Modular products

FESTO

M Mandatory data →						
Module No.	Basic function	Control function	Component size	Transport function	Connecting cable	User manual
197890	CHB	IB CB SB	F10 F30 F80	L2P R2P L4P R4P L6P R6P TU	K20 K30 K50	D E F S I
Ordering example						
197890	CHB	- SB	- F30	- L4P	- K20	- D

Ordering table				
		Conditions	Code	Enter code
M	Module No.	197890		
↓	Basic function	Checkbox family	CHB	CHB
	Control function	Identbox	-IB	
		Countbox	-CB	
		Sortbox	-SB	
	Component size	Part size Ø 0.5 ... 10 mm, part length 3 mm and above	-F10	
		Part size Ø 3 ... 30 mm, part length 3 mm and above	-F30	
		Part size Ø 3 ... 80 mm, part length 5 mm and above	-F80	
	Transport function	2 reject positions, belt transport direction: to the left	-L2P	
		2 reject positions, belt transport direction: to the right	-R2P	
		4 reject positions, belt transport direction: to the left	1-L4P	
		4 reject positions, belt transport direction: to the right	1-R4P	
		6 reject positions, belt transport direction: to the left	1-L6P	
		6 reject positions, belt transport direction: to the right	1-R6P	
		No reject positions and conveyor belt	2-TU	
	Connecting cable	Cable length 2 m	-K20	
		Cable length 3 m	-K30	
		Cable length 5 m	-K50	
	User manual	German	-D	
		English	-E	
		French	-F	
Spanish		-S		
Italian		-I		

1 L4P, R4P, L6P, R6P

Not in combination with component size F80.

2 TU

Not in combination with component size F10.

Transfer order code

197890 CHB - - - - -

Checkbox CHB

Ordering data – Modular products

FESTO

Options			
Additional function	Field of view	Guiding bar material	Alternative conveyor belt
EC	V10 V20 V33	VA	BTA BTB
- EC	- V33	- VA	- BTA

Ordering table					
			Condition s	Code	Enter code
↓	Additional function	Encoder		-EC	
0	Field of view	Adjustment of field of view to 10 mm	4	-V10	
		Adjustment of field of view to 20 mm	4	-V20	
		Adjustment of field of view to 33 mm	5	-V33	
	Guiding bar material	Stainless steel		-VA	
	Alternative conveyor belt	Conveyor belt with longitudinal ridges	6	-BTA	
		Conveyor belt with longitudinal recesses	6	-BTB	

- 4 V10, V20 Not in combination with component size F10, F80.
 5 V33 Not in combination with component size F10, F80.

- 6 BTA, BTB Not in combination with component size F80.

Transfer order code

-		-		-		-	
---	--	---	--	---	--	---	--

Software to meet individual requirements

CheckKon




Performance characteristics

Using this software the processes within the Checkbox can be displayed, logged and adapted from the camera image evaluation through to the I/O parameters.

This means:

- Transfer of new programs to the Checkbox
- Display and editing of system parameters
- Display of the evaluation of the last inspected parts recorded
- Display and logging of part contour and characteristics derived
- Display and print-out of system configuration

CheckOpti



Performance characteristics



“CheckOpti” is used in cases where the standard Checkbox learning program reaches its limits due to the fact that contour differences are too small, meaning that part orientation or quality features cannot be reliably recognised.




“CheckOpti” facilitates a complete analysis of the Checkbox recognition processes based upon contour data for the parts to be checked.

Additional, high performance test features can be defined and optimised if necessary. The new configuration can be subsequently transferred to the Checkbox.

Further product information

→ Internet: sbox-q

Ordering data – Software				
	Version	Language	Part No.	Type
	CheckKon software	German, english	194496	P.SW-KON
	CheckOpti software	German, english	568339	P.SW-OPTI

Ordering data				
	Application	Connection	Cable length [m]	Part No. Type
DUO cable			Technical data ➔ Internet: km12-duo	
	Connect buffer zone sensors	Straight plug, M12x1, 4-pin 2x straight socket, M8x1, 3-pin	0.6	18685 KM12-DUO-M8-GDGD
Connecting cable			Technical data ➔ Internet: km12-m12	
	Connect buffer zone sensors	Straight plug, M12x1, 4-pin Straight socket, M12x1, 4-pin	2.5	18684 KM12-M12-GSGD-2,5
			5	18686 KM12-M12-GSGD-5
Programming cable			Technical data ➔ Internet: kdi	
	On diagnosis	Straight socket, M12x1, 4-pin Straight socket, Sub-D, 9-pin	5	150268 KDI-SB202-BU9

Checkbox CHB

Sample applications

FESTO

Application examples


Orientation detection and quality inspection of lipstick tubes

The part check is carried out at a speed of 30 parts/s directly in a centrifuge.

The Checkbox controls the complete feed process, e.g. the start and switch-off reaction of the centrifuge or the rejection of incorrectly orientated or faulty parts.

The following features are checked:

- Orientation on the basis of a chamfer
- Length
- Diameter




Orientation detection and type identification of valve springs

Checking valve springs and controlling the integrated turning station for the supply in a measuring and marking system. The Checkbox distinguishes reliably more than 100 spring types and by means of an electronic type memory permits conversion by the pressing of a button.

The following features are checked:

- Orientation
- Length
- Diameter



Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com