

Toothed belt axes ELGR

FESTO



Toothed belt axes ELGR

Key features

FESTO

At a glance

- Ideal price/performance ratio
- Ready-to-install unit for quick and easy configuration
- Excellent reliability thanks to tested service life of 5,000 km
- Motor assembly possible on 4 sides with identical mounting accessories
- Complete kit for simple and space-saving solution for end-position sensing
- Plain-bearing guide
 - For small loads
 - Operating behaviour with torque load = Average
 - Guide backlash = 0.05 mm (on delivery)
- Recirculating ball bearing guide
 - For medium loads
 - Operating behaviour under torque load = Very good
 - Backlash-free guide (preloaded guide elements)


Applications

- Pick and Place with effective loads of up to 15 kg
- Positioning and handling with low process forces
- Actuation of guard doors in processing machines

Characteristic values of the axes

The specifications shown in the table are maximum values.

The precise values for each of the variants can be found in the relevant technical data.

Version	Size	Working stroke [mm]	Speed [m/s]	Repetition accuracy [mm]	Feed force [N]	Guide characteristics				
						Forces and torques				
						F _y [N]	F _z [N]	M _x [Nm]	M _y [Nm]	M _z [Nm]
	35	50 ... 800	3	±0.1	50	50	50	2.5	20	20
	45	50 ... 1,000	3	±0.1	100	100	100	5	40	40
	55	50 ... 1,500	3	±0.1	350	300	300	15	124	124

Note

PositioningDrives
sizing software
www.festo.com

Toothed belt axes ELGR

Key features

Complete system comprising toothed belt axis, motor, motor controller and motor mounting kit

Toothed belt axis with recirculating ball bearing or plain-bearing guide



Motor

→ 18



- 1 Servo motor EMMS-AS
- 2 Stepper motor EMMS-ST



Note

A range of specially adapted complete solutions is available for the toothed belt axis ELGR and the motors.

Motor controller

Technical data → Internet: motor controller



- 1 Servo motor controller CMMP-AS, CMMS-AS
- 2 Stepper motor controller CMMS-ST



Motor mounting kit

→ 18

Axial kit




Kit comprising:

- Motor flange
- Coupling housing
- Coupling
- Screws
- Slot nuts

Toothed belt axes ELGR

Peripherals overview

FESTO



Toothed belt axes ELGR

Peripherals overview

Variants and accessories		
Type	Brief description	→ Page/Internet
1 Slot cover NC	<ul style="list-style-type: none"> For protecting against ingress of dirt 	20
2 Centring sleeve ZBH	<ul style="list-style-type: none"> For centring loads and attachments on the slide 2 centring sleeves included in the scope of delivery of the axis 	20
3 Profile mounting MA	For mounting the axis on the bearing cap	19
4 Slot nut NM	For mounting attachments	20
5 Switching lug SA, SB	For sensing the slide position	19
6 Sensor bracket SA, SB	Adapter for mounting the inductive proximity sensors on the axis	19
7 Proximity sensor, slot type 8 SA, SB	<ul style="list-style-type: none"> Inductive proximity sensor, for slot type 8 The order code SA, SB includes 1 switching lug and 1 sensor bracket in the scope of delivery 	20
8 Drive shaft EA	<ul style="list-style-type: none"> Can be used as an alternative interface if required The axis/motor combinations → 18 do not require a drive shaft 	20
9 Motor EMMS	Motors specially matched to the axis, with or without brake	18
10 Axial kit EAMM	For axial motor mounting (comprising: coupling, coupling housing and motor flange)	18
– Connecting cable NEBU	For proximity sensor (order code SA and SB)	20

Toothed belt axes ELGR

Type codes

FESTO

		ELGR	-	TB	-		-	45	-	500	-	30H	-	L	-	
Type																
ELGR	Linear axis															
Drive function																
TB	Toothed belt															
Guide																
-	Recirculating ball bearing guide															
GF	Plain-bearing guide															
Size																
Stroke [mm]																
Stroke reserve																
Slide																
-	Slide Standard															
L	Slide, long															
Additional slide																
-	No additional slide															
ZR	1 slide on right															
ZL	1 slide on left															
ZB	1 slide on right, 1 slide on left															

Toothed belt axes ELGR

Type codes


→		2SA		4NM	EA	2MA
Proximity sensor						
...SA	Proximity sensor (SIES), inductive, slot type 8, PNP, N/O contact, cable 7.5 m					
...SB	Proximity sensor (SIES), inductive, slot type 8, PNP, N/C contact, cable 7.5 m					
Cover						
...NC	For mounting slot					
Slot nut						
...NM	For mounting slot					
Drive shaft						
...EA	Drive shaft					
Profile mounting						
...MA	Profile mounting					

Toothed belt axes ELGR

Technical data


FESTO

Function



-N- Size
35 ... 55
-T- Stroke length
50 ... 1,500 mm

[www.festo.com/en/
Spare_parts_service](http://www.festo.com/en/Spare_parts_service)



General technical data				
Size		35	45	55
Constructional design		Electromechanical linear axis with toothed belt		
Guide		Recirculating ball bearing guide		
		Plain-bearing guide		
Mounting position		Any		
Working stroke	[mm]	50 ... 800	50 ... 1,000	50 ... 1,500
Max. feed force F_x	[N]	50	100	350
Max. no-load torque	[Nm]	0.1	0.2	0.4
Max. driving torque	[Nm]	0.46	1.24	5
Max. no-load resistance to displacement	[N]	10.8	16.1	27.9
Max. speed				
Recirculating ball bearing guide	[m/s]	3		
Plain-bearing guide	[m/s]	1		
Max. acceleration ¹⁾	[m/s ²]	50		
Repetition accuracy	[mm]	±0.1		

1) The max. acceleration is dependent on the moving load, the driving torque and the max. feed force

Operating and environmental conditions			
Ambient temperature			
Recirculating ball bearing guide	[°C]	-10 ... +50	
Plain-bearing guide	[°C]	0 ... +40	
Degree of protection		IP20	
Duty cycle	[%]	100	

Weight [kg]			
Size	35	45	55
Recirculating ball bearing guide			
Basic weight with 0 mm stroke ¹⁾			
Slide standard	1.5	3.2	5.4
Slide long	1.9	4.3	7.4
Additional weight per 1,000 mm stroke	2.5	5.0	7.8
Moving load	0.5	1.1	1.9
Slide			
Slide standard	0.5	1.0	1.8
Slide long	0.8	1.7	3.0
Additional slide	0.4	0.9	1.7

1) Incl. slide

Toothed belt axes ELGR

Technical data

Weight [kg]			
Size	35	45	55
Plain-bearing guide			
Basic weight with 0 mm stroke ¹⁾			
Slide standard	1.4	3.1	5.1
Slide long	1.9	4.3	7.3
Additional weight per 1,000 mm stroke	2.5	5.0	7.8
Moving load	0.4	0.9	1.5
Slide			
Slide standard	0.4	0.9	1.5
Slide long	0.7	1.6	2.8
Additional slide	0.3	0.7	1.3

1) Incl. slide

Toothed belt			
Size	35	45	55
Pitch [mm]	2	3	3
Tensile stress [%]	0.094	0.08	0.21
Width [mm]	10	15	19.3
Effective diameter [mm]	18.46	24.83	28.65
Feed constant [mm/rev.]	58	78	90

Mass moment of inertia			
Size	35	45	55
J ₀			
Slide standard [kg mm ²]	40.26	155.13	360.48
Slide long [kg mm ²]	66.50	271.52	638.74
J _S per metre stroke [kg mm ² /m]	0.26	1.06	1.88
J _L per kg working load [kg mm ² /kg]	85.19	154.13	205.21
J _W Additional slide [kg mm ²]	36.75	136.55	301.92


The mass moment of inertia J_A of the entire axis is calculated as follows:

$$J_A = J_0 + K \times J_W + J_S \times \text{working stroke [m]} + J_L \times \text{m effective load [kg]}$$

K = Number of additional slides

Materials

Sectional view



Axis	
1 Bearing cap, profile	Wrought aluminium alloy, anodised
2 Guide rods	Steel
3 Slide, profile	Wrought aluminium alloy, anodised
4 Toothed belt	Polychloroprene with glass cord and nylon coating
5 Belt pulley	High-alloy stainless steel
Note on materials	
RoHS-compliant	
Contains PWIS (paint-wetting impairment substances)	

Toothed belt axes ELGR


Technical data

FESTO

Characteristic load values

The indicated forces and torques refer to the centre of the guide. The point of application of force is the point where the centre of the guide and the longitudinal centre of the slide intersect.

These values must not be exceeded during dynamic operation. Special attention must be paid to the cushioning phase.



If the axis is subjected to more than two of the indicated forces and torques simultaneously, the following equation must be satisfied in addition to the indicated maximum loads:

Calculating the load comparison factor:

$$f_v = \frac{|F_{y,dyn}|}{F_{y,max.}} + \frac{|F_{z,dyn}|}{F_{z,max.}} + \frac{|M_{x,dyn}|}{M_{x,max.}} + \frac{|M_{y,dyn}|}{M_{y,max.}} + \frac{|M_{z,dyn}|}{M_{z,max.}} \leq 1$$

Permissible forces and torques for a service life of 5,000 km						
Guide	Plain-bearing guide			Recirculating ball bearing guide		
Size	35	45	55	35	45	55
$F_{y,max.}, F_{z,max.}$ [N]	50	100	300	50	100	300
Slide standard						
$M_{x,max.}$ [Nm]	1	2.5	5	2.5	5	15
$M_{y,max.}$ [Nm]	4	8	16	8	16	48
$M_{z,max.}$ [Nm]	4	8	16	8	16	48
Slide long						
$M_{x,max.}$ [Nm]	1	2.5	5	2.5	5	15
$M_{y,max.}$ [Nm]	10	20	40	20	40	124
$M_{z,max.}$ [Nm]	10	20	40	20	40	124

Service life


The service life of the guide depends on the load. To provide a rough indication of the service life of the

guide, the graph below plots the load comparison factor f_v against the service life.

This graph only shows theoretical values. Consultation with your local contact person at Festo is mandatory

for load comparison factors f_v greater than 1.5.

Load comparison factor f_v as a function of service life



Example:

A user wants to move an X kg load. Using the above calculation gives a value of 1.5 for the load comparison factor f_v . According to the graph, the guide would have a service life of

approx. 1,500 km. Reducing the acceleration reduces the M_z and M_y values. A load comparison factor of 1 now gives a service life of 5,000 km.


Note

PositioningDrives
sizing software
www.festo.com


Toothed belt axes ELGR

Technical data

Max. load with flat mounting position




The characteristics in the graph correspond to the max. recommended deflection of 0.5 mm.
In this case, the axis can no longer support the maximum load past a certain stroke length.




— ELGR-TB-35
- - - ELGR-TB-45
- · - ELGR-TB-55

Maximum acceleration a as a function of applied load m


ELGR-35



ELGR-45



ELGR-55



— Horizontal
- - - Vertical


Toothed belt axes ELGR

Technical data


FESTO

Feed force F_x as a function of input torque M


ELGR-35




ELGR-45



ELGR-55



Speed v as a function of rotational speed n



— ELGR-TB-35
 - - - ELGR-TB-45
 - · - ELGR-TB-55

Toothed belt axes ELGR


Technical data

Min. nominal stroke

With standard slide or long slide L with additional slide ZR/ZL/ZB

Size	35			45			55		
Variant	-/L	ZR/ZL	ZB	-/L	ZR/ZL	ZB	-/L	ZR/ZL	ZB
Min. nominal stroke [mm]	50	126	202	50	146	242	50	166	282

Stroke reserve



L18 = Nominal stroke

L19 = Stroke reserve

- The stroke reserve is a safety distance available on both sides of the axis in addition to the nominal stroke
- The sum of the stroke length and 2x the stroke reserve must not exceed the maximum working stroke
- The stroke reserve length can be freely selected
- The stroke reserve is defined in the modular product system using the "Stroke reserve" feature.

Example:

Type ELGR-TB-45-500-20H-...

Nominal stroke = 500 mm


2x stroke reserve = 40 mm

Total stroke = 540 mm

(540 mm = 500 mm + 2x 20 mm)

Working stroke reduction

With standard slide or extra-long slide L with additional slide ZR/ZL/ZB



L7 = Slide length

L16 = Distance between both slides

L17 = Additional slide length

- For a toothed belt axis with additional slide, the working stroke is reduced by the length of the additional slide and the distance between both slides
- When ordering the extra-long slide L variant, the additional slide is not extended

Example:

Type ELGR-TB-35-500-...-ZR

Working stroke without additional slide = 500 mm

L16 = 10 mm


L7, L17 = 76 mm

Working stroke with additional slide = 414 mm
(500 mm - 10 mm - 76 mm)

Dimensions – Additional slide

Size	35	45	55
Length L17 [mm]	76	96	116
Distance between the slides L16 [mm]	≥ 0		

2nd moment of area



Size	35	45	55
I _y [mm ⁴]	3.77x10 ³	1.57x10 ⁴	3.83x10 ⁴
I _z [mm ⁴]	1.89x10 ⁵	8.08x10 ⁵	1.85x10 ⁶

Recommended deflection limits

Adherence to a maximum deflection of 0.5 mm is recommended so as not to impair the functional performance

of the axes. Greater deformation can result in increased friction, greater wear and reduced service life.


Toothed belt axes ELGR

Technical data

FESTO


Dimensions

Download CAD Data → www.festo.com/us/cad




Profile


ELGR-35



ELGR-45



ELGR-55



Toothed belt axes ELGR

Technical data

FESTO

Size	B1	B2	B3	B4	B5	B6	B7	D1 Ø H7	D2 Ø	D3 Ø H7	D4 Ø H7	H1	H2	H3	H4	H5	H6	H7	H8	H9
ELGR-35	37	35	20	7.5	9.5	1	17.5	8	15	27	7	80	39	78	19	40	7.5	63	39	21
ELGR-35-L																				
ELGR-45	47	45	20	12.5	14.5		22.5	10	20	38		117	57.5	115	32.5	50	12.5	90	57.5	34.5
ELGR-45-L																				
ELGR-55	57	55	30	12.5	14.5		27.5	16	25	48		137	67.5	135	32.5	70	12.5	110	67.5	34.5
ELGR-55-L																				

Size	H10	H11	H12	H13	H14	H15	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10	n	T1	T2	T3
																				+0.1
ELGR-35	9.5	15.5	13.5	49	23.5	20	178	89	51	25.5	3	45	76	70	30	20	1	3.1	1.6	1.6
ELGR-35-L							248	124					146	140		40	2			
ELGR-45	14.5	23	21	71	34.5	25	219	108	60	30		54	96	90	40	25	1	3	1.7	
ELGR-45-L							309	153					186	180		50	2			
ELGR-55	14.5	25.5	23.5	86	42	35	243	120	62	31		56	116	110	40	35	1	4.5	2	
ELGR-55-L							353	175					226	220		70	2			


Toothed belt axes ELGR

Ordering data – Modular products


FESTO

Order code


Mandatory data



O top L left
U underneath V front
R right H rear



Accessories



NC

MA

NM

SA, SB

SA, SB

EA

Servo motor EMMS-AS
Stepper motor EMMS-ST
→ 18

Axial kit
→ 18

Toothed belt axes ELGR

Ordering data – Modular products

Ordering table									
Size		35	45	55	Condition s	Code		Enter code	
[M]	Module No.	560505	560506	560507					
	Design	Linear axis				ELGR		ELGR	
	Drive type	Toothed belt				-TB		-TB	
[O]	Guide	Recirculating ball bearing guide							
		Plain-bearing guide				-GF			
[M]	Sizes	35	45	55		-...			
	Stroke length [mm]	50 ... 800	50 ... 1,000	50 ... 1,500	[1]	-...			
	Stroke reserve [mm]	0 ... 999 (0 = no stroke reserve)			[1]	-...H			
[O]	Slide design	Standard slide							
		Slide, long				-L			
	Additional slide	No additional slide							
		1 slide on right			[2]	-ZR			
		1 slide on left			[2]	-ZL			
		1 slide on right, 1 slide on left			[2]	-ZB			
Accessories	Accessories enclosed separately				+		+		
	Proximity sensor (SIES), inductive, slot type 8, PNP, N/O contact, cable 7.5 m, incl. switching lug and sensor bracket	1 ... 6				...SA			
	Proximity sensor (SIES), inductive, slot type 8, PNP, N/C contact, cable 7.5 m, incl. switching lug and sensor bracket	1 ... 6				...SB			
	Mounting slot cover	–	1 ... 50 (1=2 pieces, 500 mm in length)			...NC			
	Slot nut for mounting slot	1 ... 99				...NM			
	Drive shaft	1 ... 4				...EA			
	Profile mounting	1 ... 2				...MA			

[1] -... The sum of the stroke length and 2x the stroke reserve in mm must not exceed the maximum stroke length

[2] **ZR, ZL, ZB** Working stroke reduction → 13

Size	35	45	55
Variant	-/L	ZR/ZL	ZB
Min. nominal stroke [mm]	50	126	202
	50	146	242
	50	166	282






Transfer order code

	ELGR	-	TB	-		-		-		-		+							
--	------	---	----	---	--	---	--	---	--	---	--	---	--	--	--	--	--	--	--

Toothed belt axes ELGR

Accessories

FESTO


Permissible axis/motor combinations with axial kit – Without gear unit				
Motor	Axial kit	Axial kit comprising:		
		Motor flange	Coupling	Coupling housing
				
Type	Part No. Type	Part No. Type	Part No. Type	Part No. Type
ELGR-35				
With servo motor				
EMMS-AS-55-S-...	1133400 EAMM-A-R27-55A	558176 EAMF-A-38A-55A	557999 EAMD-19-15-9-8X10	1133397 EAMK-A-R27-38A
With stepper motor				
EMMS-ST-57-S-...	1133403	560692	561292	1133397
EMMS-ST-57-M-...	EAMM-A-R27-57A	EAMF-A-38A-57A	EAMD-16-15-6.35-8X10	EAMK-A-R27-38A
ELGR-45				
With servo motor				
EMMS-AS-70-S-...	1133401	558018	558000	1133398
EMMS-AS-70-M-...	EAMM-A-R38-70A	EAMF-A-38A-70A	EAMD-25-22-11-10X12	EAMK-A-R38-38A
With stepper motor				
EMMS-ST-87-S-...	1133404	560693	558000	1133398
EMMS-ST-87-M-...	EAMM-A-R38-87A	EAMF-A-38A-87A	EAMD-25-22-11-10X12	EAMK-A-R38-38A
ELGR-55				
With servo motor				
EMMS-AS-100-S-...	1133402 EAMM-A-R48-100A	558020 EAMF-A-48A-100A	558002 EAMD-42-40-19-16X25	1133399 EAMK-A-R48-48A
With stepper motor				
EMMS-ST-87-S-...	1133405	560695	558001	1133399
EMMS-ST-87-M-...	EAMM-A-R48-87A	EAMF-A-48A-87A	EAMD-32-32-11-16X20	EAMK-A-R48-48A
EMMS-ST-87-L-...				

Toothed belt axes ELGR

Accessories

Profile mounting MUE (order code: MA)

Material:
Anodised aluminium
RoHS-compliant




Dimensions and ordering data								
For size	B1	B2	B3	D1 Ø	H1	H2	H3	H4
35	51	8	43	3.4	78	6	5.5	2.3
45	69	12	57	5.5	115	10	9	3.2
55	79	12	67	5.5	135	10	9	3.2

For size	H5	L1	L2	L3	L4	Weight [g]	Part No.	Type
35	11	40	20	94	86	20	558042	MUE-50
45	17.5	52	40	139	127	32	562238	MUE-45
55	17.5	52	40	159	147	32	562238	MUE-45

Sensor bracket EAPM-...-SHS, switching lug EAPM-...-SLS (order code SA/SB)

Material:
Switching lug: Galvanised steel
Sensor bracket: Wrought aluminium
alloy, anodised
RoHS-compliant







Dimensions and ordering data						
For size	B1	H1	L1	Weight [g]	Part No.	Type
Sensor bracket						
35, 45, 55	9	6.5	44	20	567537	EAPM-L4-SHS
Switching lug						
35, 45, 55	10	11	57.5	15	567538	EAPM-L4-SLS

Toothed belt axes ELGR



Accessories



FESTO

Ordering data						
	For size	Comment	Order code	Part No.	Type	PU ¹⁾
Drive shaft EAMB						
	35	Alternative interface	EA	558034	EAMB-16-7-8X15-8X10	1
	45			558035	EAMB-18-9-8X16-10X12	
	55			558036	EAMB-24-6-15X21-16X20	
Slot nut NST						
	35	For mounting slot	NM	558045	NST-3-M3	1
	45, 55			150914	NST-5-M5	1
Centring sleeve ZBH ²⁾						
	35, 45, 55	For slide	–	186717	ZBH-7	10
Slot cover ABP						
	45, 55	For mounting slot every 0.5 m	NC	151681	ABP-5	2

1) Packaging unit quantity

2) 2 centring sleeves included in the scope of delivery of the axis

Ordering data – Proximity sensors for T-slot, inductive						Technical data → Internet: sies	
	Type of mounting	Electrical connection	Switching output	Cable length [m]	Order code	Part No.	Type
N/O contact							
	Insertable in slot from above, flush with cylinder profile	Cable, 3-wire	PNP	7.5	SA	551386	SIES-8M-PS-24V-K-7,5-OE
		Plug, M8x1, 3-pin		0.3	–	551387	SIES-8M-PS-24V-K-0,3-M8D
		Cable, 3-wire	NPN	7.5	–	551396	SIES-8M-NS-24V-K-7,5-OE
		Plug, M8x1, 3-pin		0.3	–	551397	SIES-8M-NS-24V-K-0,3-M8D
N/C contact							
	Insertable in slot from above, flush with cylinder profile	Cable, 3-wire	PNP	7.5	SB	551391	SIES-8M-PO-24V-K-7,5-OE
		Plug, M8x1, 3-pin		0.3	–	551392	SIES-8M-PO-24V-K-0,3-M8D
		Cable, 3-wire	NPN	7.5	–	551401	SIES-8M-NO-24V-K-7,5-OE
		Plug, M8x1, 3-pin		0.3	–	551402	SIES-8M-NO-24V-K-0,3-M8D

Ordering data – Connecting cables					Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type	
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541333	NEBU-M8G3-K-2.5-LE3	
			5	541334	NEBU-M8G3-K-5-LE3	
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541338	NEBU-M8W3-K-2.5-LE3	
			5	541341	NEBU-M8W3-K-5-LE3	

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com