

Valve terminals VTUB-12


FESTO



Valve terminals VTUB-12

Key features

FESTO



Innovative

- Cost-effective I-Port interface for fieldbus nodes (CTEU)
- IO-Link mode for direct connection to a higher-level IO-Link master
- Lower installation costs thanks to multi-pin plug connection
- Valve terminal for a wide range of pneumatic applications
- Minimal space requirement
- Great flexibility during planning, assembly and operation
- Pneumatic distributor integrated on the valve terminal
- Suitable for use in dusty environments

Versatile

- Room for expansion with up to 35 valve positions on one valve terminal
- Flexibility of the pneumatic working ports provides a practical solution to different requirements
- Quick and easy replacement of fittings
- Optional manifold rail variant with LED signal status display
- Wall or H-rail mounting
- Subsequently expandable to up to 18 pressure zones
- Additional supply possible when an increased air rate is required

Reliable

- Manual override
- Durable
- Sturdy thanks to the polymer housing and metal manifold rail

Easy to mount

- Ready-to-install and tested unit
- Lower ordering, installation and commissioning costs
- Wall or H-rail mounting
- Quick and secure installation thanks to integrated QS push-in connectors
- Easy valve assembly with just one screw

Note

Ordering system for valve terminal VTUB-12

➔ Internet: vtub-12


Fieldbus CTEU

➔ Internet: cteu

Valve terminals VTUB-12

Key features

FESTO



Equipment options

Valve functions

- 5/2-way valve, single solenoid
- 5/2-way valve, double solenoid
- 3/2-way valve, closed
- 3/2-way valve, open

Electrical connection options

Multi-pin plug

- Sub-D, 25-pin
- Sub-D, 44-pin
- 2 ... 35 valve positions/
max. 35 solenoid coils

I-Port


- Fieldbus connection (CTEU)
- IO-Link mode
- 3 ... 35 valve positions/
max. 35 solenoid coils

Valve terminals VTUB-12

Key features

FESTO

Pneumatic distributor



The pneumatic distributor supplies the operating pressure from port 1 to up to four other ports. The pneumatic

distributor has integrated QS4 or QS6 connections.

Note

Number of pneumatic distributors that can be used

➔ P. 34 Pilot air supply

Selector plate/pilot control with external pilot air (optional)




The VTUB-12 is intended for use with internal pilot air. It can be operated with external pilot air by mounting the

selector plate VABF-C8-12-P6-...-Z instead of the blanking

plate. The pilot air is then supplied via port 12/14 on the selector plate.

Manifold rail with multi-pin plug connection




The manifold rail features a groove into which the semi in-line valves are latched and secured with just one screw.

The valve functions 3/2-way normally open or closed, 5/2-way single solenoid and 5/2-way double solenoid are available.

The valves can be supplied as semi in-line valves with cartridges QSP for tubing diameters 4 and 6 mm.


Manifold rail with optional LED signal status display



The manifold rail with multi-pin plug can optionally be ordered with LEDs (code L).

These indicate the signal states of the solenoid coils.

Manifold rail with I-Port interface




The manifold rail can be ordered with I-Port interface (code PT) and IO-Link (code LK) as a basis for fieldbus

nodes (CTEU) or in IO-Link mode for direct connection to a higher-level IO-Link master.

Valve terminals VTUB-12

Key features

Sub-base for semi in-line valve



The valve VUVB-12 can be operated as an individual valve using an individual sub-base (single width for single solenoid valves or double width

for double solenoid valves). The power is supplied via the plug socket with cable KMYZ and the adapter (M8x1)

with corresponding connecting cable (→ accessories, p. 34).

Blanking plate





Plate without valve function for reserving valve positions on a valve terminal.

Valves and blanking plates are attached to the manifold rail using one screw.


Pressure zone supply module



The pressure zone supply module occupies one valve position and can be used as an additional supply or for supplying a pressure zone.

The pressure zone supply module is attached to the manifold rail using one screw.

Separator for duct separation



Pressure zone separation can be realised in duct 1 in the manifold rail. Up to 18 pressure zones can be created on the valve terminal in this way.

There must be at least 2 valve positions between 2 separators.

Valve terminals VTUB-12

Key features

FESTO

Integration of the I-Port interface/IO-Link

Different fieldbus nodes are used for integration into the control systems of various manufacturers.


The following protocols are supported with the compatible fieldbus node CTEU:

- CANopen
- DeviceNet

- EtherCAT
- CC-Link
- PROFIBUS

Use of the adapter CAPC permits decentralised installation of fieldbus nodes CTEU on a further valve terminal or input modules with I-Port interfaces (→ installation system CTEU/CTEL)

System overview, example



- Communication with higher-order controller via fieldbus

- Use fieldbus node CTEU compatible with the fieldbus protocol


- Up to 64 inputs/outputs (solenoid coils), depending on the valve terminal

Valve terminals VTUB-12

Peripherals overview

Overview – Valve terminal VTUB-12 with multi-pin plug connection, Sub-D

- Up to 20 valve positions/solenoid coils, 25-pin Sub-D multi-pin plug connection, code: M
 - From 21 valve positions/solenoid coils, 44-pin Sub-D multi-pin plug connection, code: M
- Valve terminals with electrical multi-pin plug connection are available with 2 to max. 35 valve positions.
- Each valve position can either be equipped with a valve, a pressure zone supply module or a blanking plate. Double solenoid valves occupy two valve positions.
- A maximum of 35 solenoid coils can be actuated via the electrical multi-pin plug connection. Up to 18 pressure zones are possible.



Accessories			Brief description	→ Page/Internet
1	Connecting cable	NEBV	Connecting cable for multi-pin plug connection, with Sub-D plug	36
2	Push-in fitting	QS	For connecting compressed air tubing with standard O.D.	37
3	Selector plate	VABF	Pilot control with external pilot air (optional)	35
4	Pneumatic distributor	VABF	For connecting additional distributors to the air supply (port 1)	34
5	Blanking plate	VABB	Blanking plate for vacant position (pneumatic distributor)	34
6	Silencer	U	For venting hole	37
7	Solenoid valve	VUVB-12	–	33
8	Pressure zone supply module	VABF	For supplying pressure zones or for additional air supply	34
9	Blanking plate	VABB	Blanking plate for vacant position (solenoid valve)	34
10	Silencer	U	For fitting in exhaust ports	37
11	Fittings	QS	For connecting compressed air tubing with standard O.D.	37
12	Blanking plug	B	For sealing the air supply port	35
13	Manifold rail	VABM	With multi-pin plug connection, for connecting max. 35 valves	33
	Separator	VABD	For duct separation in duct 1, for creating pressure zones	35

Valve terminals VTUB-12

Peripherals overview

FESTO

Overview – Valve terminal VTUB-12 with I-Port interface/IO-Link


- Up to 35 valve positions/solenoid coils
- I-Port interface connection type, code: PT
- IO-Link connection type, code: LK

The electrical supply/transmission of communication data takes place via an M12 plug. The valve terminal can be equipped with 3 ... 35 valves. Up to 18 pressure zones are possible.

Each valve position can either be equipped with a valve, a pressure zone supply module or a blanking plate. Double solenoid valves occupy two valve positions.

The following protocols are supported when using the associated fieldbus node CTEU:

- DeviceNet
- CANopen
- PROFIBUS DP
- EtherCAT
- CC-Link



Accessories		Brief description	→ Page/Internet
1	Bus node	CTEU	–
2	Plug	SEA	For IO-Link and load voltage
3	T-adaptor	FB	For IO-Link and load voltage (in combination with plug SEA for separate load voltage)
4	Pneumatic distributor	VABF	For connecting additional distributors to the air supply (port 1)
5	Push-in fitting	QS	–
6	Selector plate	VABF	Pilot control with external pilot air (optional)
7	Blanking plate	VABB	Blanking plate for vacant position (pneumatic distributor)
8	Silencer	U	For venting hole
9	Solenoid valve	VUVB-12	–
10	Pressure zone supply module	VABF	For supplying pressure zones or for additional air supply
11	Blanking plate	VABB	Blanking plate for vacant position (solenoid valve)
12	Silencer	U	For fitting in exhaust ports
13	Fittings	QS	For connecting compressed air tubing with standard O.D.
14	Blanking plug	B	For sealing the air supply port
15	Manifold rail	VABM	With I-Port interface, for connecting max. 35 valves
	Separator	VABD	For duct separation in duct 1, for creating pressure zones


Valve terminals VTUB-12

Peripherals overview

FESTO

Sub-base for semi in-line valve

- Single design for single solenoid valves
 - Double design for double solenoid valves
- Electrical connection via plug socket with cable KMYZ and adapter (M8x1) with corresponding connecting cable.




Accessories			Brief description	→ Page/Internet
1	Single solenoid valve	VUVB-12	–	33
2	Double solenoid valve	VUVB-12	–	33
3	Push-in fitting	QS	For port 2, 4: cartridge with push-in connector	37
4	Sub-base	VABS	Double design for individual double solenoid valve	34
5	Sub-base	VABS	Single design for individual single solenoid valve	34
6	Silencer	AMTC	For port 3, 5 (optional)	37
7	Push-in fitting	QS	For port 1: cartridge with push-in connector	37
8	Push-in fitting	QS	For port 12, 14: cartridge with push-in connector (optional)	37
9	Adapter	VAVE	M8x1 (optional), LED	38
10	Plug socket with cable	KMYZ	Connecting cable (optional)	36
11	Inscription label holder	IBS-6x10	–	35

Valve terminals VTUB-12

Key features – Pneumatic components


FESTO

Wide range of pneumatic components




- The use of the same basic valves for the 3/2-way and 5/2-way valve function permits fast and flexible conversion and multiple use of parts.
- Flexible construction thanks to assembled and tested units or individual components as modules for individual configurations.
- Flow rates from 230 ... 400 l/min depending on the valve used and appropriate QS connections.

Changing fittings on port 2/4



The cartridges (port 2/4) can be changed quickly and easily by removing the spring clip. The ports can be sealed by inserting a blanking plug (→ 35).

Connection to the valve



- T (on top, inline)
- TA (on top, angled outlet to the front)
- TB (on top, angled outlet to the front/rear)
- TC (on top, angled outlet to the rear)

Connection sizes:

- Push-in connector 4 mm (code P4)
- Push-in connector 6 mm (code P6)

Pilot air supply

Internal

The port for the pneumatic main supply is located on the left-hand sub-base (multi-pin plug connection/I-Port interface).

The internal pilot air (duct 12/14) is branched from duct 1 in the left-hand sub-base.

The air is branched using a pneumatic distributor or a blanking plate on the left-hand pneumatic distributor port. The multi-pin plug connection provides two pneumatic distributor ports and the I-Port interface provides one.

External

External pilot air is supplied via the selector plate on the left-hand pneumatic distributor port. It enables the pilot air and main supply to the valve terminal to be separated.

The multi-pin plug connection provides one pneumatic distributor port and the I-Port interface does not provide any.

Valve terminals VTUB-12

Key features – Pneumatic components

Creating pressure zones

Up to 18 pressure zones can be created using the separator VABD-C8 ... if different working pressures are required. The separators are inserted at the required location in duct 1 in the manifold rail and screwed into place.

The following rules apply:

- Two pressure zones can be realised without an additional pressure zone supply module (VABF-C8 ...) if


there is a compressed air supply at both ends. Only one separator in duct 1 is required for this.

- A pressure zone supply module (VABF-C8 ...) is additionally required after the third pressure zone; this module occupies one valve position.
- There must be at least 2 valve positions between 2 separators.

Note

- Pressure zones can be freely configured with the VTUB-12.
- Duct separation does not result in any valve positions being lost, however valve positions will be lost if an additional supply is required.
- If a valve terminal with duct separation is ordered via the configurator, the duct separation comes already labelled.
- Older manifold rails predating approx. mid-2013 cannot be retrofitted for the purpose of creating pressure zones.
- Further information on assembly → Assembly instructions for VABD-C8-P1-D2

Duct separation



Description

Duct separation and creation of pressure zones

- Remove the end plate.
- Insert an Allen key (size 4) from above at the required position in duct 1 in the manifold rail as a stop.

- Using another Allen key, push separator VABD-C8 ... into duct 1 as far as it will go until it is in the appropriate position and then turn the Allen key to secure in place.
- Fit the end plate.
- Affix the enclosed symbol labels to the duct separation.

Design

Valve replacement





The valves are attached to the aluminium manifold rail using one screw, which means that they can be easily

replaced. Use of high-quality plastics guarantees minimum weight and maximum performance.

Expansion

Blanking plates can be replaced by valves at a later date. The dimensions, mounting points and the pneumatic

installation already carried out do not change.


Valve function				
Code	Circuit symbol	Width		Description
		12 mm	24 mm	
M		■	–	5/2-way valve, single solenoid <ul style="list-style-type: none"> • Mechanical spring return • Non-reversible • Not suitable for vacuum
J		–	■	5/2-way valve, double solenoid <ul style="list-style-type: none"> • Non-reversible • Not suitable for vacuum
N		■	–	3/2-way valve, single solenoid <ul style="list-style-type: none"> • Normally open • Mechanical spring return • Non-reversible • Not suitable for vacuum
K		■	–	3/2-way valve, single solenoid <ul style="list-style-type: none"> • Normally closed • Mechanical spring return • Non-reversible • Not suitable for vacuum

Valve terminals VTUB-12

Key features – Display and operation

FESTO

Display and operation




- 1 Manual override (non-detenting, non-detenting/detenting)
- 2 Screw for valve assembly

The manual override enables the valve to be switched without electronic control or power supply.


Manual override

Manual override with automatic reset (non-detenting)



Press in the stem of the manual override with a pointed object or screwdriver.
 → The valve is switched.
 Remove the pointed object or screwdriver.
 Spring force pushes the stem of the manual override back.
 → Valve returns to normal position.

Manual override with lock (non-detenting/detenting)



Press in the stem of the manual override with a pointed object or screwdriver until the valve switches and then turn the stem clockwise by 90° until the stop is reached.
 → The valve remains switched.
 Turn the stem anti-clockwise by 90° until the stop is reached and then remove the pointed object or screwdriver. Spring force pushes the stem of the manual override back.
 → Valve returns to normal position.

Note

A manually operated valve (manual override) cannot be reset electrically. Conversely, a solenoid actuated valve

cannot be reset using the mechanical manual override.

Valve terminals VTUB-12


Key features – Assembly

Valve terminal assembly

Sturdy valve terminal assembly thanks to:


- Through-holes for wall mounting
- H-rail mounting

Wall mounting



Sturdy terminal assembly thanks to four through-holes for wall mounting (M5 screws).

H-rail mounting



The H-rail mounting VAME-T-M5 consists of two mounting clips. These are attached to the manifold rail on the left and right (M5 screws). The lower through-holes on the manifold rail are used for this.

The valve terminal VTUB-12 prepared in this way is lowered onto the H-rail from above (arrow A) and clipped into the H-rail at the bottom (arrow B).

Note


- Note the max. tightening torque of 2 Nm ($\pm 25\%$) for the screws for mounting the H-rail.
- Only horizontal H-rail mounting is permissible.
- Mounting only possible on H-rail TH 35-15 to EN 50022.
- Vibration/shock loads are not permissible with H-rail mounting.

Valve terminals VTUB-12

Key features – Electrical components

FESTO

Multi-pin plug connection




Control signals from the controller to the valve terminal are transmitted via a pre-assembled multi-core cable, which substantially reduces installation time.

This valve terminal can be equipped with 2 ... 35 valves.

Versions

- Sub-D connection

I-Port interface/IO-Link



IO-Link

IO-Link is an interface that supplies data for communication in addition to the power supply.

An IO-Link system consists of an IO-Link master and IO-Link devices. The IO-Link master offers the interface to the higher-order controller (PLC) and controls communication with the connected IO-Link devices.


One device with IO-Link (e.g. an IO-Link valve terminal from Festo) can be connected to each port on an IO-Link master.

I-Port

The Festo-specific I-Port interface based on IO-Link offers the following connection options:

- Directly at the fieldbus, by mounting a fieldbus node CTEU
- Connection to a higher-order I-Port master from Festo

Overview




Valve terminals VTUB-12

Key features – Electrical components

FESTO

Protective circuit

Manifold rail with LED signal status display, multi-pin plug connection



Note

The electrical protective circuit only relates to the optional LED variant with the multi-pin plug connection.

Electrical multi-pin plug connection

The following multi-pin plug connections are available for the valve terminal VTUB-12:

- Sub-D multi-pin plug connection (25-pin)
- Sub-D multi-pin plug connection (44-pin)

Pins 1 ... 44 are used for addresses 0 ... 43 in order.

If fewer than 44 addresses are used for the valve terminal, the remaining pins are left free. Pins 22 ... 25 or 41 ... 44 are reserved for the neutral conductor or 24 V respectively.

The valves are switched by means of positive or negative logic (positive switching or negative switching). Mixed operation is not permitted.

Each pin on the multi-pin plug can actuate exactly one solenoid coil. If the maximum configurable number of valve positions is 35, then 35 valves can be addressed with one solenoid coil (single solenoid).

Note

A double solenoid valve occupies two valve positions. With 17 or more valve positions, the number of available valve positions for double solenoid valves decreases.

Pin allocation – Sub-D plug, 25-pin

	Pin	Address/coil	15-wire, NEBV-S1...25-K-...-LE15	25-wire, NEBV-S1...25-K-...-LE25
			Wire colour ¹⁾ of connecting cable	
	1	0	WH	WH
	2	1	BN	BN
	3	2	GN	GN
	4	3	YE	YE
	5	4	GY	GY
	6	5	PK	PK
	7	6	BU	BU
	8	7	RD	RD
	9	8	BK	BK
	10	9	VT	VT
	11	10	GY PK	GY PK
	12	11	RD BU	RD BU
	13	12	–	GN WH
	14	13	–	BN GN
	15	14	–	YE WH
	16	15	–	BN YE
	17	16	–	GY WH
	18	17	–	BN GY
	19	18	–	WH PK
	20	19	–	BN PK
Note The drawing shows the view onto the pins of the Sub-D plug.	21	–	–	BU WH
	22	0 V/24 V	–	BN BU
	23	0 V/24 V	GN WH	RD WH
	24	0 V/24 V	BN GN	BN RD
	25	0 V/24 V	YE WH	BK WH


1) To IEC 757

Valve terminals VTUB-12

Key features – Electrical components

FESTO

Pin allocation – Sub-D plug, 44-pin


NEBV-S1...44-K-...-LE39							
	Pin	Address	Wire colour ¹⁾ Connecting cable		Pin	Address	Wire colour ¹⁾ Connecting cable
	1	0	WH		23	22	WH RD
	2	1	BN		24	23	BN RD
	3	2	GN		25	24	WH BK
	4	3	YE		26	25	BN BK
	5	4	GY		27	26	GY GN
	6	5	PK		28	27	YE GY
	7	6	BU		29	28	PK GN
	8	7	RD		30	29	YE PK
	9	8	BK		31	30	GN BU
	10	9	VT		32	31	YE BU
	11	10	GY PK		33	32	GN RD
	12	11	RD BU		34	33	YE RD
	13	12	WH GN		35	34	GN BK
	14	13	BN GN		36	–	–
	15	14	WH YE		37	–	–
	16	15	YE BN		38	–	–
	17	16	WH GY		39	–	–
	18	17	GY BN		40	–	–
	19	18	WH PK		41	0 V	YE BK
	20	19	PK BN		42	0 V	GY BU
	21	20	WH BU		43	0 V	PK BU
	22	21	BN BU		44	0 V	GY RD

Note

The drawing shows the view onto the pins of the Sub-D plug.

1) To IEC 757

Pin allocation – Sub-D plug, 44-pin

NEBV-S1...44-K-...-LE44							
	Pin	Address	Wire colour ¹⁾ Connecting cable		Pin	Address	Wire colour ¹⁾ Connecting cable
	1	0	WH		23	22	WH RD
	2	1	BN		24	23	BN RD
	3	2	GN		25	24	WH BK
	4	3	YE		26	25	BN BK
	5	4	GY		27	26	GY GN
	6	5	PK		28	27	YE GY
	7	6	BU		29	28	PK GN
	8	7	RD		30	29	YE PK
	9	8	BK		31	30	GN BU
	10	9	VT		32	31	YE BU
	11	10	GY PK		33	32	GN RD
	12	11	RD BU		34	33	YE RD
	13	12	WH GN		35	34	GN BK
	14	13	BN GN		36	35	YE BK
	15	14	WH YE		37	35	GY BU
	16	15	YE BN		38	37	PK BU
	17	16	WH GY		39	38	GY RD
	18	17	GY BN		40	39	PK RD
	19	18	WH PK		41	0 V	GY BK
	20	19	PK BN		42	0 V	PK BK
	21	20	WH BU		43	0 V	BU BK
	22	21	BN BU		44	0 V	RD BK

Note



The drawing shows the view onto the pins of the Sub-D plug.

1) To IEC 757


Valve terminals VTUB-12

Key features – Electrical components

FESTO

Pin allocation – Adapter M8x1 with LED		
	Pin	
Round plug, M8, 3-pin		
	VAVE-C8-1R8	
	1	Not used
	3	0 V
	4	24 V
Round plug, M8, 4-pin		
	VAVE-C8-1R1	
	1	Not used
	2	Not used
	3	0 V
	4	24 V

1) To DIN EN 61076-2-101




I-Port interface/IO-Link		
<p>The valve terminal VTUB-12 can be connected as follows via the I-Port connection:</p> <ul style="list-style-type: none">• Directly to the fieldbus by mounting the CTEU bus node on the valve terminal• To an IO-Link master (in IO-Link mode) via a cable	<p>Up to 35 solenoid coils can be actuated. A valve position always occupies one address. The following assignment applies in this case:</p> <ul style="list-style-type: none">– Less significant valve position (address) for coil 14– More significant valve position (address) for coil 12	<p>Addresses are allocated in ascending order without gaps, from left to right. The address allocation is independent of whether blanking plates or valves are used.</p>
		<p>Note</p> <p>More information on CTEU ➔ cteu</p> <p>Additionally required IODD for IO-Link mode ➔ www.festo.com</p>

Note

More information on CTEU
→ cteu

Additionally required IODD for IO-Link mode
→ www.festo.com

Pin allocation of the I-Port/IO-Link cable ¹⁾		
	Pin	Allocation
	1	24 V electronics (logic voltage)
	2	24 V valves (load voltage)
	3	0 V electronics (logic)
	4	COM I-Port communication signal
	5	0 V valves (load)

1) 5-pin socket, M12, A-coded

Valve terminals VTUB-12

Key features – Applications

FESTO

Equipment

Operate system equipment with unlubricated compressed air if possible. Festo valves and cylinders are designed so that, if used as intended, they will not require additional lubrication and will still achieve a long service life. The compressed air prepared with the compressor must correspond in quality to unlubricated compressed air. If possible, do not operate all of your system equipment with lubricated compressed air. The lubricators should, where possible, always be installed directly upstream of the actuator used.

Incorrect additional oil and too high an oil content in the compressed air reduce the service life of the valve terminal.
Use Festo special oil OFSW-32 or the alternatives listed in the Festo catalogue (as specified in DIN 51524 HLP32; basic oil viscosity 32 CST at 40 °C).

Bio-oils

When using bio-oils (oils which are based on synthetic or native ester, e.g. rapeseed oil methyl ester), the maximum residual oil content of 0.1 mg/m³ must not be exceeded (see ISO 8573-1 Class 2).

Mineral oils

When using mineral oils (e.g. HLP oils to DIN 51524, parts 1 to 3) or similar oils based on poly-alpha-olefins (PAO), the maximum residual oil content of 5 mg/m³ must not be exceeded (see ISO 8573-1 Class 4). A higher residual oil content irrespective of the compressor oil cannot be permitted, as the basic lubricant would be flushed out over time.

Valve terminals VTUB-12

Technical data – Valve terminal VTUB-12 with multi-pin plug connection

FESTO

Voltage

24 V DC

Pressure

+2.8 ... +8 bar

Temperature range

–5 ... +60 °C



General technical data				
Valve function		3/2C	3/2U	5/2-way, single solenoid
Design		Poppet valve with spring return		
Valve function		Closed	Open	Single solenoid
Sealing principle		Soft		
Actuation type		Electric		
Reset method		Mechanical spring		
Type of control		Piloted		
Pilot air supply		Internal		
		External		
Direction of flow		Non-reversible		
Exhaust function		No flow control		
Manual override		Non-detenting, non-detenting/detenting		
Type of mounting		Via through-hole		
Width		[mm]		24
Nominal size		[mm]		4
Max. number of valve positions		35		17
Max. number of pressure zones		18		
Standard nominal flow rate		qnN	[l/min]	400
Pneumatic connection		1, 3, 5	G1/4	
		2, 4	QS-4 or QS-6	
		12, 14	G1/8	

Operating and environmental conditions						
Valve function			3/2C	3/2U	5/2-way, single solenoid	5/2-way, double solenoid
Operating medium			Compressed air to ISO 8573-1:2010 [7:4:4]			
Note on operating/pilot medium			Lubricated operation possible (in which case lubricated operation will always be required)			
Operating pressure	Internal pilot air	[bar]	+2 ... +8	+2.8 ... +8		
	External pilot air	[bar]	0 ... +8			
Pilot pressure		[bar]	+2 ... +8	+2.8 ... +8		
Ambient temperature		[°C]	−5 ... +60			
Temperature of medium		[°C]	−5 ... +60			
CE marking			To EU EMC Directive			

Valve terminals VTUB-12

FESTO

Technical data – Valve terminal VTUB-12 with multi-pin plug connection

Product weight		
Approx. weight		[g]
Valves		
• 5/2-way single solenoid (code M), ducted solenoid exhaust		27.8
• 5/2way double solenoid (code J), ducted solenoid exhaust		57.4
• 5/2-way single solenoid (code M), unducted solenoid exhaust		27.5
• 5/2-way double solenoid (code J), unducted solenoid exhaust		57.1
• 3/2-way closed (code K), ducted/unducted solenoid exhaust		26.3
• 3/2-way open (code N), unducted solenoid exhaust		28.1
• 3/2-way open (code N), ducted solenoid exhaust		29.4
Manifold rail		
• Multi-pin plug with Sub-D plug, 25-pin	2 valve positions	382
	4 valve positions	484
	6 valve positions	585
	8 valve positions	687
	10 valve positions	788
	12 valve positions	890
	14 valve positions	992
	16 valve positions	1,093
	18 valve positions	1,195
	20 valve positions	1,296
	24 valve positions	1,500
	28 valve positions	1,704
	32 valve positions	1,907
	35 valve positions	2,060
• Multi-pin plug with Sub-D plug, 44-pin		
Blanking plate for vacant position		13.8
Pressure zone supply module for pressure zones or additional supply		13.8
Separator for duct separation		9.8
Pneumatic distributor Q4, Q6, Q4-Q6		65.6, 59, 62.3
Blanking plate for pneumatic distributor		8.4
Selector plate		38.8
Sub-base for individual valve, single width		15
Sub-base for individual valve, double width		30

Electrical data		
Nominal operating voltage	[V DC]	24, reverse polarity protected
Permissible voltage fluctuations		±10%
Electrical power consumption per solenoid coil	[W]	1
Protection class to EN 60529		IP65
Duty cycle	[%]	100

Materials	
Manifold rail	Wrought aluminium alloy
Solenoid valve housing	PA reinforced
Solenoid valve seals	NBR, TPE-U
Solenoid valve piston spool	Wrought aluminium alloy
Blanking plate housing, additional supply housing	PA reinforced
Separator for duct separation	Beryllium bronze, brass
Pneumatic distributor, pneumatic distributor blanking plate	PA reinforced
Selector plate	Wrought aluminium alloy
Sub-base for individual valve	PA reinforced
Note on materials	RoHS-compliant

Valve terminals VTUB-12

Technical data – Valve terminal VTUB-12 with I-Port interface, IO-Link

FESTO

Voltage


24 V DC

Pressure

+2.8 ... +8 bar

Temperature range

–5 ... +60 °C



General technical data				
Valve function	3/2C	3/2U	5/2-way, single solenoid	5/2-way, double solenoid
Design	Poppet valve with spring return			Poppet valve with self-holding function
Valve function	Closed	Open	Single solenoid	Double solenoid
Sealing principle	Soft			
Actuation type	Electric			
Reset method	Mechanical spring			–
Type of control	Piloted			
Pilot air supply	Internal			
	External			
Direction of flow	Non-reversible			
Exhaust function	No flow control			
Manual override	Non-detenting, non-detenting/detenting			
Type of mounting	Via through-hole			
Width	[mm]	12		24
Nominal size	[mm]	4		
Max. number of valve positions		35	35	17
Max. number of pressure zones		18		
Standard nominal flow rate	qnN	[l/min]	400	
Pneumatic connection	1, 3, 5	G1/4		
	2, 4	QS-4 or QS-6		
	12, 14	G1/8		

Operating and environmental conditions				
Valve function	3/2C	3/2U	5/2-way, single solenoid	5/2-way, double solenoid
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]			
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)			
Operating pressure	Internal pilot air	[bar]	+2 ... +8	+2.8 ... +8
	External pilot air	[bar]	0 ... +8	
Pilot pressure		[bar]	+2 ... +8	+2.8 ... +8
Ambient temperature		[°C]	–5 ... +50	
Temperature of medium		[°C]	–5 ... +50	
CE marking	To EU EMC Directive			

Note

The CE marking for the valve terminal with I-Port interface applies up to a maximum connecting cable length of 30 m.

Valve terminals VTUB-12

FESTO

Technical data – Valve terminal VTUB-12 with I-Port interface, IO-Link

Product weight		
Approx. weight		[g]
Valves		
• 5/2-way single solenoid (code M), ducted solenoid exhaust		27.8
• 5/2way double solenoid (code J), ducted solenoid exhaust		57.4
• 5/2-way single solenoid (code M), unducted solenoid exhaust		27.5
• 5/2-way double solenoid (code J), unducted solenoid exhaust		57.1
• 3/2-way closed (code K), ducted/unducted solenoid exhaust		26.3
• 3/2-way open (code N), unducted solenoid exhaust		28.1
• 3/2-way open (code N), ducted solenoid exhaust		29.4
• I-Port interface with M12 plug	4 valve positions	521
	6 valve positions	627
	8 valve positions	727
	10 valve positions	834
	12 valve positions	940
	14 valve positions	1,040
	16 valve positions	1,145
	18 valve positions	1,251
	20 valve positions	1,358
	24 valve positions	1,562
	28 valve positions	1,775
	32 valve positions	1,982
	35 valve positions	2,138
Blanking plate for vacant position		13.8
Pressure zone supply module for pressure zones or additional supply		13.8
Separator for duct separation		9.8
Pneumatic distributor Q4, Q6, Q4-Q6		65.6, 59, 62.3
Blanking plate for pneumatic distributor		8.4
Selector plate		38.8
Sub-base for individual valve, single width		15
Sub-base for individual valve, double width		30

Electrical data		
Nominal operating voltage	[V DC]	24, reverse polarity protected
Permissible voltage fluctuations		±10%
Electrical power consumption per solenoid coil	[W]	1
Protection class to EN 60529		IP65
Duty cycle	[%]	100
Intrinsic current consumption, logic supply	[mA]	30
Intrinsic current consumption, valve supply	[mA]	30
Max. cable length	[m]	20
Min. cable cross section	[mm ²]	1
Baud rate	COM3	[kbps] 230.4
	COM2	[kbps] 38.4

Materials	
Manifold rail	Wrought aluminium alloy
Solenoid valve housing	PA reinforced
Solenoid valve seals	NBR, TPE-U
Solenoid valve piston spool	Wrought aluminium alloy
Blanking plate housing, additional supply housing	PA reinforced
Separator for duct separation	Beryllium bronze, brass
Pneumatic distributor, pneumatic distributor blanking plate	PA reinforced
Selector plate	Wrought aluminium alloy
Sub-base for individual valve	PA reinforced
Note on materials	RoHS-compliant


Valve terminals VTUB-12

Technical data


FESTO

Valve switching times [ms]			
Valve function	3/2-way	5/2-way, single solenoid	5/2-way, double solenoid
On	6	6	–
Off	14	14	–
Changeover	–	–	10


Pilot pressure as a function of operating pressure
(operating pressure with external pilot air),
pilot pressure 5/2 and 3/2U



Pilot pressure as a function of operating pressure
(operating pressure with external pilot air),
pilot pressure 3/2C



Flow rate q per valve with multiple (n) valves switched simultaneously
(tolerance ± 20%)




Valve terminals VTUB-12

Technical data

FESTO

Materials

Sectional view – Valves



1	Housing	PA reinforced
2	Piston spool	Wrought aluminium alloy
–	Seals	NBR, PUR
–	Manifold rail with multi-pin plug	Wrought aluminium alloy
–	Pressure zone supply module	PA reinforced
–	Blanking plate for vacant position	PA reinforced
–	Selector plate	Wrought aluminium alloy


Valve terminals VTUB-12

Technical data

FESTO

Dimensions – 3/2-way valve, single solenoid, normally open


Download CAD Data → www.festo.com/us/cad



Type	B1	B2	B3	B4	B5	H1	H2	H3	H4	L1	L2	L3	L4	L5	L6
VUVB-ST12-M32U-...-QX-1T1	12	11.7	9.8	6.5	3.5	24	18.4	14.5	2.5	89.6	65.3	57.8	34.7	20.2	20.5
VUVB-ST12-M32U-...-QX-D-1T1										89.9					20.8

Dimensions – 3/2-way valve, single solenoid, normally closed

Download CAD Data → www.festo.com/us/cad



Type	B1	B2	B3	B4	B5	H1	H2	H3	H4	L1	L2	L3	L5	L6
VUVB-ST12-M32C-...-QX-1T1	12	11.7	9.8	6.5	3.5	24	18.5	14.5	2.5	89.6	65.3	57.8	34.8	20.5
VUVB-ST12-M32C-...-QX-D-1T1										89.9				20.8


Valve terminals VTUB-12

Technical data

FESTO

Dimensions – 5/2-way valve, single solenoid


Download CAD Data → www.festo.com/us/cad



Type	B1	B2	B3	B4	B5	B6	B7	H1	H2	H3	H4	L1	L2	L3	L4	L5	L6	L7
VUVB-ST12-M52-MZH-QX-1T1	–	–	12	9.8	–	6.5	3.5	24	18.5	14.5	2.5	89.6	–	65.3	57.8	34.7	20.2	20.5
VUVB-ST12-M52-MZH-QX-D-1T1												89.9						20.8

Dimensions – 5/2-way valve, double solenoid

Download CAD Data → www.festo.com/us/cad




Type	B1	B2	B3	B4	B5	B6	B7	H1	H2	H3	H4	L1	L2	L3	L4	L5	L6	L7
VUVB-ST12-B52-ZH-QX-1T1	23.7	21.8	12	9.8	14.6	6.5	6	24	18.5	14.5	2.5	92.4	89.5	68.1	60.7	37.6	23.1	20.5
VUVB-ST12-B52-ZH-QX-D-1T1												92.7	89.8					20.8

Valve terminals VTUB-12

Technical data



Dimensions – Manifold rail with multi-pin plug Download CAD Data → www.festo.com/us/cad



Type	B1	B2	B3	B4	B5	B6	B7	D1	D2	H1	H2	H3	H4
VABM-C8-12E	100	87	61.4	55.9	31.5	31.3	14.5	G1/4	5.5	49	42.2	33	14.5

Type	L1	L2	L3	L4	L5	L6	L7	L8	L9
VABM-C8-12E	(n x 12) + 107	(n x 12) + 20	(n x 12) + 11	41.5	36	20	12	10	4.5


Valve terminals VTUB-12

Technical data

FESTO

Dimensions – Manifold rail with I-Port interface

Download CAD Data → www.festo.com/us/cad



Type	B1	B2	B3	B4	B5	B6	B7	D1	D2-Ø	H1	H2	H4	H5
VTUB-12	100	87	61.5	55.9	31.5	31.3	14.5	G1/4	5.5	48	42.2	14.5	13.5

Type	L1	L2	L3	L5	L6	L7	L8	L9
VTUB-12	(nx12)+100	(nx12)+20	(nx12)+11	36	20	12	10	4.5

Valve terminals VTUB-12


Technical data

FESTO

Dimensions – Valve terminal

Download CAD Data → www.festo.com/us/cad

With electrical multi-pin plug



- | | | | |
|---|--|---------------------------------------|---|
| 1 5/2-way valve | 4 Sub-D plug, 25-pin or 44-pin
with 21 or more solenoid coils | 6 Hole for wall mounting,
Ø 5.5 mm | 7 Fittings for air supply port
n Number of valve positions
(2 ... 35) |
| 2 Blanking plate for vacant
position | 5 Silencer, threaded connection
G $\frac{1}{4}$ | | |
| 3 Silencer, threaded connection
M5 | | | |

Type	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10	L11	L12	L13	L14	L15	L16	L17
VTUB-12	(n x 12) + 107 ±1.5	(n x 12) + 20	(n x 12) + 11	78	71.5	67	32.4 ±1	42.5	40 ±1	25.7	24.5	23.7	20	11.7	10.2	7.2	4.5

Type	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	D1	H1	H2	H12	H13
VTUB-12	103 ±2	100.4 ±1.1	86.5	61.5	55.9	40.5	31.5	31.5	14.5	2.8	G $\frac{1}{4}$	88.2 ±1	82 ±1	14.5	2.5

Valve terminals VTUB-12


Technical data

FESTO

Dimensions – Valve terminal

Download CAD Data → www.festo.com/us/cad

With I-Port interface, fieldbus node CTEU



Type	B2	B3	B4	B5	B7	B8	B9	B10	D1	H1	H2	H11	H12	H13
VTUB-12	100	87	61.5	55.9	31.3	31.5	14.5	3	$G\frac{1}{4}$	88.2	82	14.5	13.5	2.5

Type	L1	L2	L3	L4	L5	L6	L9	L11	L12	L13	L14	L15	L16	L17
VTUB-12	(nx12)+100	(nx12)+20	(nx12)+11	78	64.5	60	40	24.5	23.7	20	11.7	10.2	7.2	4.5


Valve terminals VTUB-12

Technical data

FESTO

Dimensions – Sub-base for semi in-line valve (single solenoid)


Download CAD Data → www.festo.com/us/cad



- | | | | |
|--|---|---|--|
| 1 Connecting cable (optional) | 4 Plug socket with cable KMYZ (optional) | 7 Port 3, 5: silencer AMTC-P-PC10 (optional) | 9 Exhaust port 82/84 |
| 2 Adapter M8x1 (optional) | 5 Port 12, 14: cartridge with push-in connector (optional) | 8 Holes for M4 mounting | 10 Mounting space for spring clips for solenoid valve |
| 3 Port 2, 4: cartridge with push-in connector | 6 Port 1: cartridge with push-in connector | | 11 Mounting space for spring clips for sub-base |
| | | | 12 Slot for inscription label IBS6x10 (not included in the scope of delivery) |

Type	B1	B2	H1	H2	H3	H4	H5	H6	L1	L2	L3	L4	L5	L6	L7	L8	L9	L10	L11	L12	W1
VABS-C8-12XB-QX-B	12.6	11.9	34.9	30.6	17.9	15.5	11	6.9	94.5	82.9	57.3	50	37.3	30	22.8	15.5	9.5	8.3	82	51	60°
VABS-C8-12XB-QX																					







Technical data



Valve terminals VTUB-12

Accessories





FESTO




Ordering data					
	Code	Valve function	Solenoid exhaust air	Part No.	Type
Solenoid valves					
	M	5/2-way valve, single solenoid, manual override non-detenting	Unducted	557649	VUVB-ST12-M52-MZH-QX-1T1
			Ducted	558369	VUVB-ST12-M52-MZH-QX-D-1T1
		5/2-way valve, single solenoid, manual override non-detenting/detenting	Unducted	570908	VUVB-ST12-M52-MZD-QX-1T1
			Ducted	570909	VUVB-ST12-M52-MZD-QX-D-1T1
	Y	5/2-way valve, double solenoid, manual override non-detenting	Unducted	557650	VUVB-ST12-B52-ZH-QX-1T1
			Ducted	558370	VUVB-ST12-B52-ZH-QX-D-1T1
		5/2-way valve, double solenoid, manual override non-detenting/detenting	Unducted	570910	VUVB-ST12-B52-ZD-QX-1T1
			Ducted	570911	VUVB-ST12-B52-ZD-QX-D-1T1
	K	3/2-way valve, single solenoid, closed, manual override non-detenting	Unducted	575997	VUVB-ST12-M32C-MZH-QX-1T1
			Ducted	575998	VUVB-ST12-M32C-MZH-QX-D-1T1
		3/2-way valve, single solenoid, closed, manual override non-detenting/detenting	Unducted	576001	VUVB-ST12-M32C-MZD-QX-1T1
			Ducted	576002	VUVB-ST12-M32C-MZD-QX-D-1T1
	N	3/2-way valve, single solenoid, open, manual override non-detenting	Unducted	575999	VUVB-ST12-M32U-MZH-QX-1T1
			Ducted	576000	VUVB-ST12-M32U-MZH-QX-D-1T1
		3/2-way valve, single solenoid, open, manual override non-detenting/detenting	Unducted	576003	VUVB-ST12-M32U-MZD-QX-1T1
			Ducted	576004	VUVB-ST12-M32U-MZD-QX-D-1T1
Manifold rail					
	–	Multi-pin plug with Sub-D plug, 25-pin	2	557651	VABM-C8-12E-G14-2-M1
			4	557653	VABM-C8-12E-G14-4-M1
			6	557655	VABM-C8-12E-G14-6-M1
			8	557657	VABM-C8-12E-G14-8-M1
			10	557659	VABM-C8-12E-G14-10-M1
			12	557661	VABM-C8-12E-G14-12-M1
			14	557663	VABM-C8-12E-G14-14-M1
			16	557665	VABM-C8-12E-G14-16-M1
			18	557667	VABM-C8-12E-G14-18-M1
			20	557669	VABM-C8-12E-G14-20-M1
		Multi-pin plug with Sub-D plug, 44-pin	24	557673	VABM-C8-12E-G14-24-M1
			28	557677	VABM-C8-12E-G14-28-M1
			32	557681	VABM-C8-12E-G14-32-M1
			35	557684	VABM-C8-12E-G14-35-M1
	L	Multi-pin plug with Sub-D plug, 25-pin, LED signal status display	2	1361863	VABM-C8-12E-G14-2-M1-L
			4	1361865	VABM-C8-12E-G14-4-M1-L
			6	1361867	VABM-C8-12E-G14-6-M1-L
			8	1361868	VABM-C8-12E-G14-8-M1-L
			10	1361869	VABM-C8-12E-G14-10-M1-L
			12	1361870	VABM-C8-12E-G14-12-M1-L
			14	1361871	VABM-C8-12E-G14-14-M1-L
			16	1361873	VABM-C8-12E-G14-16-M1-L
			18	1361874	VABM-C8-12E-G14-18-M1-L
			20	1361875	VABM-C8-12E-G14-20-M1-L
		Multi-pin plug with Sub-D plug, 44-pin, LED signal status display	24	1361876	VABM-C8-12E-G14-24-M1-L
			28	1361877	VABM-C8-12E-G14-28-M1-L
			32	1361878	VABM-C8-12E-G14-32-M1-L
			35	1361879	VABM-C8-12E-G14-35-M1-L

Valve terminals VTUB-12

Accessories







FESTO



Ordering data					
	Code	Description	Valve positions	Part No.	Type
Manifold rail					
	PT/LK	Manifold rail with I-Port interface	4	1247975	VABM-C8-12E-G14-4-PT-L
			6	1247976	VABM-C8-12E-G14-6-PT-L
			8	1247977	VABM-C8-12E-G14-8-PT-L
			10	1247978	VABM-C8-12E-G14-10-PT-L
			12	1247979	VABM-C8-12E-G14-12-PT-L
			14	1247980	VABM-C8-12E-G14-14-PT-L
			16	1247981	VABM-C8-12E-G14-16-PT-L
			18	1247982	VABM-C8-12E-G14-18-PT-L
			20	1247983	VABM-C8-12E-G14-20-PT-L
			24	1247984	VABM-C8-12E-G14-24-PT-L
			28	1247985	VABM-C8-12E-G14-28-PT-L
			32	1247986	VABM-C8-12E-G14-32-PT-L
			35	1247987	VABM-C8-12E-G14-35-PT-L
Sub-base for individual valve					
	–	Internal pilot air supply	1 (M52/M32)	1236025	VABS-C8-12XB-QX-B
		External pilot air supply	1 (M52/M32)	1236027	VABS-C8-12XB-QX
	–	Internal pilot air supply	1 (B52)	1236028	VABS-C8-12XB-QX-DB
		External pilot air supply	1 (B52)	1236029	VABS-C8-12XB-QX-D
Pressure zone supply module					
	S	For additional air supply or for supplying pressure zones	1	1894888	VABF-C8-12-P3A5-QX

Ordering data				
	Code	Description	Part No.	Type
Blanking plate				
	L	Blanking plate for vacant valve position	562461	VABB-C8-12-ET
	–	Blanking plate for pneumatic distributor position	562460	VABB-C8-12-A
Pneumatic distributor				
	AL	Push-in connector 4 mm	562457	VABF-C8-12-V1P4-Q4
	BL	Push-in connector 6 mm	562458	VABF-C8-12-V1P4-Q6
	CL	Push-in connector 4 and 6 mm	562459	VABF-C8-12-V1P4-Q4-Q6

Valve terminals VTUB-12

Accessories






Ordering data					
	Code	Description	Packaging unit	Part No.	Type
Selector plate					
	SL	Pneumatic connection G1/8	1 piece	1210305	VABF-C8-12-P6-G18-Z
H-rail mounting					
	H	For mounting the valve terminal VTUB-12 on a standard H-rail TH 35-15 to EN 50022. (Use the following screws for mounting: M5x40 to DIN 912, 2 pieces)	2 pieces	2636436	VAME-T-M5
Separator					
	SP	For creating pressure zones (duct separation in duct 1)	1 piece	1877936	VABD-C8-P1
Blanking plug					
	–	Connection Ø 10 mm	1 piece	562243	QSPC10
	–	For thread G1/4	10 pieces	3569	B-1/4
Inscription labels					
	–	Inscription labels 6x10mm, 64 pieces, in frames	1 piece	18576	IBS-6x10

Ordering data					
	Code	Description	Cable length [m]	Part No.	Type
Connecting cables for multi-pin plug					
	M1	• Sub-D, 15-pin, straight socket, up to 12 coils, IP65	2.5	538222	NEBV-S1G25-K-2,5-N-LE15
	M2	• Open end, 15 wires	5	538223	NEBV-S1G25-K-5-N-LE15
	M3		10	538224	NEBV-S1G25-K-10-N-LE15
	M1	• Sub-D, 25-pin, straight socket, up to 24 coils, IP65	2.5	538225	NEBV-S1G25-K-2,5-N-LE25
	M2	• Open end, 25 wires	5	538226	NEBV-S1G25-K-5-N-LE25
	M3		10	538227	NEBV-S1G25-K-10-N-LE25
	M1	• Sub-D, 44-pin, straight socket, up to 35 coils, IP65	2.5	565289	NEBV-S1G44-K-2.5-N-LE39
	M2	• Open end, 40 wires	5	565290	NEBV-S1G44-K-5-N-LE39
	M3		10	565291	NEBV-S1G44-K-10-N-LE39
	M1L	• Sub-D, 25-pin, straight socket, up to 24 coils, IP40	2.5	575417	NEBV-S1G25-K-2.5-N-LE25-S6
	M2L	• Open end, 25 wires	5	575418	NEBV-S1G25-K-5-N-LE25-S6
	M3L		10	575419	NEBV-S1G25-K-10-N-LE25-S6
	M1L	• Sub-D, 44-pin, straight socket, up to 35 coils, IP40	2.5	575113	NEBV-S1G44-K-2.5-N-LE44-S6
	M2L	• Open end, 44 wires	5	575114	NEBV-S1G44-K-5-N-LE44-S6
	M3L		10	575115	NEBV-S1G44-K-10-N-LE44-S6
	MA1	• Sub-D, 25-pin, angled socket, up to 24 coils, IP65	2.5	575423	NEBV-S1WA25-K-2.5-N-LE25-S8
	MA2	• Open end, 25 wires	5	575424	NEBV-S1WA25-K-5-N-LE25-S8
	MA3		10	575425	NEBV-S1WA25-K-10-N-LE25-S8
	MA1	• Sub-D, 44-pin, angled socket, up to 35 coils, IP65	2.5	575420	NEBV-S1WA44-K-2.5-N-LE44-S8
	MA2	• Open end, 44 wires	5	575421	NEBV-S1WA44-K-5-N-LE44-S8
	MA3		10	575422	NEBV-S1WA44-K-10-N-LE44-S8

Valve terminals VTUB-12

Accessories










FESTO

Ordering data				
	Description	Cable length [m]	Part No.	Type
Plug socket with cable for individual valve				
	Angled socket, square design, 2-pin, cable open at one end, 2-wire, with LED, IP65	2.5	193687	KMYZ-9-24-2,5-LED-PUR-B
		5	193689	KMYZ-9-24-5-LED-PUR-B
		10	196063	KMYZ-9-24-10-LED-PUR-B
	Angled socket, square design, 2-pin, straight plug, M8x1, 3-pin, with LED, IP65	0.5	196064	KMYZ-9-24-M8-0,5-LED-B
		2.5	196065	KMYZ-9-24-M8-2,5-LED-B
	Angled socket, square design, 2-pin, cable with open end, 2-wire, without LED, IP40	0.5	193690	KMYZ-4-24-0,5-B
		2.5	193691	KMYZ-4-24-2,5-B
Connecting cables				
	Open cable end, 3-wire			
	Socket M8x1, straight, 3-pin	2.5	541333	NEBU-M8G3-K-2.5-LE3
		5	541334	NEBU-M8G3-K-5-LE3
		10	541332	NEBU-M8G3-K-10-LE3
		2.5	159420	SIM-M8-3GD-2,5-PU
		5	159421	SIM-M8-3GD-5-PU
		10	192964	SIM-M8-3GD-10-PU
	Socket M8x1, angled, 3-pin	2.5	541338	NEBU-M8W3-K-2.5-LE3
		5	541341	NEBU-M8W3-K-5-LE3
		10	541335	NEBU-M8W3-K-10-LE3
		2.5	159422	SIM-M8-3WD-2,5-PU
		5	159423	SIM-M8-3WD-5-PU
		10	192965	SIM-M8-3WD-10-PU
	Open cable end, 4-wire			
	Socket M8x1, straight, 4-pin	2.5	541342	NEBU-M8G4-K-2.5-LE4
		5	541343	NEBU-M8G4-K-5-LE4
		2.5	158960	SIM-M8-4GD-2,5-PU
		5	158961	SIM-M8-4GD-5-PU
	Socket M8x1, angled, 4-pin	2.5	541344	NEBU-M8W4-K-2.5-LE4
		5	541345	NEBU-M8W4-K-5-LE4
		2.5	158962	SIM-M8-4WD-2,5-PU
		5	158963	SIM-M8-4WD-5-PU
	Straight plug, 3-pin			
	Socket M8x1, straight, 3-pin	0.5	541346	NEBU-M8G3-K-0.5-M8G3
		1	541347	NEBU-M8G3-K-1-M8G3
		2.5	541348	NEBU-M8G3-K-2.5-M8G3
		5	541349	NEBU-M8G3-K-5-M8G3
		10	569844	NEBU-M8G3-K-10-M8G3
	Straight plug, 4-pin			
	Socket M8x1, straight, 3-pin	2.5	554037	NEBU-M8G3-K-2.5-M8G4
	Socket M8x1, straight, 4-pin	2.5	554035	NEBU-M8G4-K-2.5-M8G4

Valve terminals VTUB-12

Accessories


FESTO



Ordering data					
	Description	Tubing O.D.	Packaging unit	Part No.	Type
Push-in fitting					Technical data → Internet: quick star
	With sealing ring Connection G $\frac{1}{4}$	8 mm	10 pieces	186099	QS-G$\frac{1}{4}$-8
		10 mm	10 pieces	186101	QS-G$\frac{1}{4}$-10
		12 mm	10 pieces	186350	QS-G$\frac{1}{4}$-12
Push-in L-fitting					Technical data → Internet: quick star
	With sealing ring Connection G $\frac{1}{4}$	8 mm	10 pieces	186120	QSL-G$\frac{1}{4}$-8
		10 mm	10 pieces	186122	QSL-G$\frac{1}{4}$-10
		12 mm	10 pieces	186351	QSL-G$\frac{1}{4}$-12
Push-in L-fitting, long					Technical data → Internet: quick star
	With sealing ring Connection G $\frac{1}{4}$	8 mm	10 pieces	186131	QSL-G$\frac{1}{4}$-8
		10 mm	10 pieces	186133	QSL-G$\frac{1}{4}$-10
		12 mm	10 pieces	132596	QSL-G$\frac{1}{4}$-12
Cartridge with push-in connector					
	Straight Connection Ø 10 mm	4 mm	10 pieces	172972	QSP10-4
		6 mm	10 pieces	172973	QSP10-6
	L-shape Connection Ø 10 mm	4 mm	10 pieces	132601	QSPLK10-4
		6 mm	10 pieces	132602	QSPLK10-6
	L-shape, long Connection Ø 10 mm	4 mm	10 pieces	132603	QSPLLK10-4
		6 mm	10 pieces	132604	QSPLLK10-6
Silencer					
					Technical data → Internet: u
	For thread M5		1 piece	4645	U-M5
	For thread G $\frac{1}{4}$		1 piece	2316	U-$\frac{1}{4}$
	For individual sub-base, QSP10		1 piece	1224460	AMTC-P-P10








Valve terminals VTUB-12

Accessories

FESTO











Ordering data				
	Code	Description	Part No.	Type
Adapter M8x1				
	–	Plug M8x1, 3-pin, with LED	571686	VAVE-C8-1R8
	–	Plug M8x1, 4-pin, with LED	573194	VAVE-C8-1R1

Ordering data – I-Port interface/IO-Link				
	Code	Description	Cable length [m]	Part No. Type
Connection technology for IO-Link				
	XM	T-adapter M12, 5-pin	2.5	171175 FB-TA-M12-5POL
	XN	Straight plug, M12, 5-pin (in combination with adapter for separate load voltage)	2.5	175487 SEA-M12-5GS-PG7

Ordering data – CTEU				
			Part No.	Type
Bus node				
	–	CANopen fieldbus node	570038	CTEU-CO
	–	DeviceNet fieldbus node	570039	CTEU-DN
	–	CC-Link fieldbus node	1544198	CTEU-CC
	–	PROFIBUS fieldbus node	570040	CTEU-PB
	–	EtherCAT fieldbus node	572556	CTEU-EC
Bus connection				
	–	Sub-D plug, straight, for DeviceNet/CANopen	532219	FBS-SUB-9-BU-2x5POL-B
	–	Sub-D plug, straight, for CC-Link	532220	FBS-SUB-9-GS-2x4POL-B
	–	Sub-D plug, straight, for PROFIBUS	532216	FFBS-SUB-9-GS-DP-B
	–	Sub-D plug, angled, for CANopen, 9-pin	533783	FBS-SUB-9-WS-CO-K
	–	Sub-D plug, angled, for PROFIBUS, 9-pin	533780	FBS-SUB-9-WS-PB-K
	–	M12x1, 5-pin, A-coded, for DeviceNet/CANopen	525632	FBA-2-M12-5POL
	–	M12x1, 5-pin, B-coded, for PROFIBUS	533118	FBA-2-M12-5POL-RK
	–	For 5-pin terminal strip for DeviceNet/CANopen	525634	FBA-1-SL-5POL
	–	Terminal strip, 5-pin, for DeviceNet/CANopen	525635	FBSD-KL-2x5POL

Valve terminals VTUB-12

Accessories

Ordering data – CTEU		Part No.	Type
Bus connection			
	Screw terminal for CC-Link	197962	FBA-1-KL-5POL
	Fieldbus socket, M12x1, 5-pin, for DeviceNet/CANopen	18324	FBSD-GD-9-5POL
	Plug, M12x1, 5-pin, for DeviceNet/CANopen	175380	FBS-M12-5GS-PG9
	Straight socket, M12x1, 5-pin, for assembling a connecting cable compatible with FBA-2-M12-5POL-RK for PROFIBUS	1067905	NECU-M-B12G5-C2-PB
	Straight plug, M12x1, 5-pin, for assembling a connecting cable compatible with FBA-2-M12-5POL-RK for PROFIBUS	1066354	NECU-M-S-B12G5-C2-PB
	Terminating resistor, M12, B-coded for PROFIBUS	1072128	CACR-S-B12G5-220-PB
	Plug M12x1, 4-pin, D-coded for EtherCAT	543109	NECU-M-S-D12G4-C2-ET
Connecting plate			
	—	570042	CAPC-F1-E-M12
Connecting cables			
	Straight socket, M12x1, 5-pin	574321	NEBU-M12G5-E-5-Q8N-M12G5
	Straight plug, M12x1, 5-pin	574322	NEBU-M12G5-E-7.5-Q8N-M12G5
	Nominal conductor cross section 1 mm ²	574323	NEBU-M12G5-E-10-Q8N-M12G5
	Angled socket, M12x1, 5-pin	570733	NEBU-M12W5-K-0.5-M12W5
	Angled plug, M12x1, 5-pin	570734	NEBU-M12W5-K-2-M12W5
	Straight socket, M12x1, 5-pin	8003617	NEBU-M12G5-K-0.5-M12W5
	Angled plug, M12x1, 5-pin	8003618	NEBU-M12G5-K-2-M12W5
Plug socket			
	For power supply, M12x1, 5-pin, B-coded for CANopen/DeviceNet	538999	NTSD-GD-9-M12-5POL-RK
	For power supply, M12x1, 5-pin for CC-Link, PROFIBUS, EtherCAT	18324	FBSD-GD-9-5POL
Inscription label			
	For bus node	565306	ASLR-C-E4

Product Range and Company Overview

A Complete Suite and Company Overview

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support
and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors,
controllers & drivers



Pneumatics
Pneumatic linear and rotary actuators,
valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors
and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 16,000 employees in 60 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.




© Copyright 2013, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmental friendly printing plant.

Festo North America



**1 Festo Canada
Headquarters**
Festo Inc.
5300 Explorer Drive
Mississauga, ON
L4W 5G4

2 Montréal
5600, Trans-Canada
Pointe-Claire, QC
H9R 1B6

3 Québec City
2930, rue Watt#117
Québec, QC
G1X 4G3



**4 Festo United States
Headquarters**
Festo Corporation
395 Moreland Road
Hauppauge, NY
11788

5 Appleton
North 922 Tower View Drive, Suite N
Greenville, WI
54942

7 Detroit
1441 West Long Lake Road
Troy, MI
48098

6 Chicago
85 W Algonquin - Suite 340
Arlington Heights, IL
60005

8 Silicon Valley
4935 Southfront Road, Suite F
Livermore, CA
94550

Festo Regional Contact Center

Canadian Customers

Commercial Support:

Tel: 1 877 GO FESTO (1 877 463 3786)

Fax: 1 877 FX FESTO (1 877 393 3786)

Email: festo.canada@ca.festo.com

Technical Support:

Tel: 1 866 GO FESTO (1 866 463 3786)

Fax: 1 877 FX FESTO (1 877 393 3786)

Email: technical.support@ca.festo.com

USA Customers

Commercial Support:

Tel: 1 800 99 FESTO (1 800 993 3786)

Fax: 1 800 96 FESTO (1 800 963 3786)

Email: customer.service@us.festo.com

Technical Support:

Tel: 1 866 GO FESTO (1 866 463 3786)

Fax: 1 800 96 FESTO (1 800 963 3786)

Email: product.support@us.festo.com

Subject to change

Internet: www.festo.com/us