


Stopper cylinders DFST

FESTO



Stopper cylinders DFST

Key features

FESTO

At a glance

- Gentle stopping without impact vibration or noise
- Single-acting or double-acting
- Powerful shock absorber for high energy absorption
- Wide range of applications thanks to adjustable shock absorber
- Supply ports at side or underneath
- Adjustable active direction thanks to rotatable toggle lever arrangement (90°, 180°, 270°)
- Position sensing via inductive proximity sensor SIEN on the toggle lever or via proximity sensor for T-slot SME-/SMT-8 on the piston
- Sturdy design for long service life
- Stable guide rod
- Seal for protection against dirt and moisture

The technology in detail

Cushioning adjustment


- Adaptable shock absorber depending on the load on the workpiece carrier
- Easy adjustment via knurled adjusting wheel **1**
- Shock absorber can be replaced in the fitted position




Optional: toggle lever lock

- For locking the toggle lever **1**
- The toggle lever lock **2** can be ordered as a variant of the stopper cylinder or as an accessory
- Simple design
- Reliable function

Piston Ø 50:





Piston Ø 63, 80:



Toggle lever deactivator


- For deactivation of the stop function
- The toggle lever deactivator can be ordered as an accessory
- Simple design



Position sensing

- Sensing of the toggle lever position (workpiece carrier in stop position) via inductive proximity sensor SIEN-M8 **1**
- Sensing of the piston position (cylinder retracted or advanced) via proximity sensor SME-/SMT-8 in the slot **2**

Sensing of the toggle lever position



Sensing of the piston position




Stopper cylinders DFST

Key features

FESTO


Functional sequence

Step 1




1. Gentle stopping of heavy masses via a hydraulic shock absorber in the piston rod.

Step 2




2. The toggle lever (optional) is locked into the retracted end position so that the workpiece carrier cannot be pushed back by the shock absorber.

Step 3




3. The workpiece carrier is released by means of compressed air, and the toggle lever is released simultaneously.

Step 4



4. The piston is advanced by means of spring force or compressed air. The toggle lever tips back which prevents the workpiece carrier from being pushed up.

Step 5



5. The toggle lever is raised by means of spring force and stops the next workpiece carrier.

Stopper cylinders DFST

Type codes


FESTO

		DFST	-	50	-	30	-	D	L	-	Y4	-	A
Type													
DFST	Stopper cylinder												
Piston Ø [mm]													
Stroke [mm]													
Function													
	Single-acting, pulling												
D	Double-acting												
Locking													
	No												
L	Via toggle lever lock												
Cushioning													
Y4	Adjustable shock absorber												
Position sensing													
A	Via proximity sensor												

Stopper cylinders DFST

Peripherals overview

FESTO




Variants and accessories		
Type	Brief description	→ Page/Internet
1 Toggle lever deactivator DADP-TF	For deactivation of the stop function. The workpiece carrier is able to pass the stopper cylinder without activating the cylinder	15
2 Proximity sensor, inductive SIEN-M8	For sensing of the toggle lever position	15
3 Toggle lever lock DADP-TL	<ul style="list-style-type: none"> For piston \varnothing 50 For locking the toggle lever in the retracted position. With pressurisation, the workpiece carrier and the toggle lever are released simultaneously 	15
4 Toggle lever lock DADP-TL	<ul style="list-style-type: none"> For piston \varnothing 63, 80 For locking the toggle lever in the retracted position. With pressurisation, the workpiece carrier and the toggle lever are released simultaneously 	15
5 Proximity sensor SME-/SMT-8	For sensing the piston position	15
6 Plug socket with cable KMEB	–	14
7 Solenoid valve MEBH	For quick and direct actuation of the stopper cylinder	14
8 Intermediate plate ZVA-2	For attaching the valve	15

Stopper cylinders DFST

Technical data

FESTO



⌀ Diameter
50 ... 80 mm

Stroke length
30 ... 40 mm



General technical data			
Piston Ø	50	63	80
Pneumatic connection	G $\frac{1}{8}$		
Stroke [mm]	30		40
Constructional design	Piston rod with toggle lever		
Mode of operation	Double-acting		
	Single-acting, pulling		
Protection against torsion/guide	Guide rod		
Type of mounting	Via through-holes		
Cushioning (of piston movement)	Flexible cushioning rings/pads at both ends		
Position sensing	Via proximity sensor		
Mounting position	Vertical		
Product weight [g]	1,800	3,500	6,850

Operating and environmental conditions	
Operating medium	Compressed air in accordance with ISO 8573-1:2010 [7:-:-]
Operating pressure ¹⁾ [bar]	2 ... 10
Ambient temperature [°C]	5 ... 60
Corrosion resistance class CRC ²⁾	1


1) Min. operating pressure for piston Ø 50 with toggle lever lock is 3 bar

2) Corrosion resistance class 1 as per Festo standard 940 070

Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

Materials

Sectional view



Stopper cylinder		
Piston Ø	50	63, 80
1 Rollers	Polyacetate	
2 Attachments	Nickel-plated cast steel	
3 Piston rod	High-alloy stainless steel	
4 End cap	Die-cast aluminium	Wrought aluminium alloy
5 Housing	Wrought aluminium alloy	
– Seals	Nitrile rubber	
Note on materials	RoHS-compliant	


Stopper cylinders DFST

Technical data

FESTO

Braking distance


The braking distance refers to the distance from when contact is made with the toggle lever to the end stop.



Piston Ø		50	63	80
Braking distance	[mm]	14.75	14.75	20

Resetting force F_R of the toggle lever against the delivery direction


The resetting force refers to the minimum force that must be applied to press the toggle lever into the end position.



Piston Ø		50	63	80
Resetting force at the toggle lever	[N]	11	23	36

Permissible impact force F_{Impact} on the rollers of the toggle lever when the piston rod is advanced and the toggle lever is pushed into its end position

The permissible impact force refers to the momentary force that may act on the toggle lever when it is already pushed into its end position without damaging the rod bearing or the toggle lever mechanism.



Piston Ø		50	63	80
Impact force	[N]	3,000	5,000	6,000


Stopper cylinders DFST

Technical data

FESTO


Permissible mass m as a function of the conveyor speed v

The values in the graph opposite take into account a friction value of $\mu = 0.1$.



Permissible transverse force F_Q during the switching operation as a function of the pressure p

The applied load causes a transverse force to act on the piston rod. To ensure the function of the cylinder, a certain minimum pressure must be applied.



Stopper cylinders DFST


Technical data

FESTO

Selection aid

Stopping a workpiece carrier

The stopper cylinder is used to brake an individual workpiece carrier, with-out or without end position locking. The toggle lever and oil damper are pushed into the end position again for each new workpiece carrier.



Example

Given:

Friction value $\mu = 0.1$

Delivery speed $v = 20 \text{ m/min}$


Workpiece carrier with workpiece $m = 200 \text{ kg}$

Operating pressure $p = 6 \text{ bar}$

Choice: Stopper cylinder DFST-50

1. Checking the permissible mass

The maximum permissible mass at a delivery speed of 20 m/min is 250 kg . This means that the total mass of the workpiece carrier and workpiece of 200 kg is permissible.



2. Checking the permissible transverse force during the switching operation

Transverse force F_Q = friction force

F_{Friction}


$$F_{\text{Friction}} = \mu \times m \times g$$

$$= 0.1 \times 200 \text{ kg} \times 9.81 \text{ m/s}^2$$

$$= \text{approx. } 200 \text{ N}$$

The maximum permissible transverse force at an operating pressure of 6 bar is $1,000 \text{ N}$.

This means that the transverse force of 200 N is permissible.



Stopper cylinders DFST


Technical data

FESTO

Selection aid

Stopping or separating several workpiece carriers

The stopper cylinder is used to separate workpiece carriers. Further workpiece carriers accumulate behind carriers that have already pushed the toggle lever into its end position. Since the oil damper in the stopper cylinder is inoperative in this case, a certain amount of cushioning between the workpiece carriers must be guaranteed (e.g. elastomer elements).



Example

Given:

Friction value $\mu = 0.1$

Delivery speed $v = 15 \text{ m/min}$

Workpiece carrier with workpiece $m = 100 \text{ kg}$

Operating pressure $p = 6 \text{ bar}$

Maximum number of workpiece carriers accumulating simultaneously $n_{\text{Group}} = 1$

Maximum number of all queued workpiece carriers $n_{\text{Queue}} = 5$


Maximum number of all advancing workpiece carriers $n_{\text{Queue-1}} = 4$

Spring travel of the workpiece carrier buffer $s_F = 10 \text{ mm}$

Choice: Stopper cylinder DFST-50

1. Checking the permissible mass of the first workpiece carrier

The maximum permissible mass at a delivery speed of 15 m/min is 320 kg. This means that the total mass of the workpiece carrier and workpiece of 100 kg is permissible.



2a. Calculation of the maximum permissible impact force when workpiece carriers accumulate behind a carrier at the stopper cylinder

With the DFST-50, the maximum permissible impact force is 3,000 N. This means that at a total force of 1,150 N, the number of workpiece carriers is permissible.

Impact force calculation:

$$F_{\text{Impact}} = \frac{(n_{\text{Group}} \times m) \times v^2}{s_F} = \frac{(1 \times 100 \text{ kg}) \times (15 \text{ m}/60 \text{ s})^2}{0.01 \text{ m}} = \text{ca. } 650 \text{ N}$$

Friction force:

$$F_{\text{Friction}} = \mu \times (n_{\text{Queue}} \times m) \times g = 0.1 \times (5 \times 100 \text{ kg}) \times 9.81 \text{ m/s}^2 = \text{ca. } 500 \text{ N}$$

Max. total force:

$$F_{\text{Total force}} = F_{\text{Impact}} + F_{\text{Friction}} = 650 \text{ N} + 500 \text{ N} = 1150 \text{ N}$$

Stopper cylinders DFST

Technical data

FESTO


Selection aid

2b. Checking the permissible transverse force during the switching operation


Transverse force $F_Q =$
friction force F_{friction}
 $F_{\text{friction}} = 500 \text{ N}$

The maximum permissible transverse force at an operating pressure of 6 bar is 1,000 N.


This means that the transverse force of 500 N is permissible.



3. Separating and advancing the workpiece carriers



The maximum permissible mass with the DFST-50 at a delivery speed of 15 m/min is 320 kg. Since the total mass of the four workpiece carriers advancing on the stopper cylinder is 400 kg, the next largest stopper cylinder must be selected for separating.



Max. total mass:

$$m_{\text{Total force}} = n_{\text{Queue}-1} \times m = 4 \times 100\text{kg} = 400\text{kg}$$

Result

The stopper cylinder DFST-63 must be selected for separating five workpiece carriers.


Stopper cylinders DFST

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com



- 1 Supply port (retract)
- 2 Supply port (advance)
- 3 Maximum permissible underside depth of workpiece carrier


Ø	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	D1	D2	D3	D5	D6
[mm]	□	□					□				Ø	Ø			Ø
50	93	73	43	20	8	17	64	7	36	8.1	32	20	M8x1	M4	9
63	114	90	54	25	10		75			10.1	40	20			11
80	138	110	63	30	12		95			12.1	50	25			13

Ø	D7	EE	H1	H2	H3	H4	H5	H6	H7	H8	L1	L2	L3	R1	T1	T2	W1
[mm]	Ø																
50	14	G1/8	219	118	91	17.5	107.5	5	8.75	5.5	14	5	26	36.3	5	1	25
63	18		251	134	107	25	123	5	12.5	4.5	29	6	34	44.4	6	–	20
80	20		322.5	159	151	19	144	4.2	9.5	6.8	36	8	42	55.5	6	–	22

Stopper cylinders DFST

Technical data

FESTO

Ordering data					
	Piston \varnothing	with spring	without spring	with toggle lever lock	Part No. Type
	50	■			543 729 DFST-50-30-Y4-A
		■		■	555 572 DFST-50-30-L-Y4-A
			■		543 730 DFST-50-30-D-Y4-A
			■	■	555 573 DFST-50-30-DL-Y4-A
	63	■			543 744 DFST-63-30-Y4-A
		■		■	555 574 DFST-63-30-L-Y4-A
			■		543 745 DFST-63-30-D-Y4-A
			■	■	555 575 DFST-63-30-DL-Y4-A
	80	■			543 747 DFST-80-40-Y4-A
		■		■	555 576 DFST-80-40-L-Y4-A
			■		543 748 DFST-80-40-D-Y4-A
			■	■	555 577 DFST-80-40-DL-Y4-A

Stopper cylinders DFST

Accessories

FESTO









Mounting options for solenoid valves and valve functions


A solenoid valve MEH, MEBH, MOEH or MOEBH can be mounted on the stopper cylinder for quick, direct

actuation of the cylinder. The valve must be connected to the cylinder via an intermediate plate ZVA. The posi-

tion of the piston rod when the solenoid valve is in the normal position

depends on the valve type and the position of the valve on the cylinder.


Ordering data – Solenoid valve		Technical data → Internet: meh	
Mounting options for the solenoid valve with intermediate plate ZVA	Position of the piston rod in normal position	Part No.	Type
Single-acting			
		173 125	MEH-3/2-5,0-B
		172 999	MEBH-3/2-5,0-B
		173 429	MOEH-3/2-5,0-B
		173 002	MOEBH-3/2-5,0-B
Double-acting			
		173 128	MEH-5/2-5,0-B
		173 005	MEBH-5/2-5,0-B
		173 128	MEH-5/2-5,0-B
		173 005	MEBH-5/2-5,0-B




Ordering data – Plug socket with cable		Technical data → Internet: kmeb	
	For Ø	Part No.	Type
	50, 63, 80	151 688	KMEB-1-24-2,5-LED
		151 689	KMEB-1-24-5-LED
		193 457	KMEB-1-24-10-LED


Stopper cylinders DFST




Accessories

FESTO

Ordering data – Intermediate plate			
	For Ø	Part No.	Type
	50, 63, 80	164 897	ZVA-2

Ordering data			
	For Ø	Part No.	Type
Lever locking mechanism DADP-TL			
	50	543 751	DADP-TL-F3-50
	63	543 752	DADP-TL-F3-63
	80	543 753	DADP-TL-F3-80
Free pass mechanism DADP-TF			
	50	543 755	DADP-TF-F3-50
	63	543 756	DADP-TF-F3-63
	80	543 757	DADP-TF-F3-80




Ordering data – Proximity sensor, inductive				Technical data → Internet: sien	
	For Ø	Contact	Electrical connection	Part No.	Type
	50, 63, 80	N/O contact	Cable, 2.5 m	150 386	SIEN-M8B-PS-K-L
			Plug	150 387	SIEN-M8B-PS-S-L
		N/C contact	Cable, 2.5 m	150 390	SIEN-M8B-PO-K-L
			Plug	150 391	SIEN-M8B-PO-S-L



Ordering data – Proximity sensor for T-slot, magneto-resistive					Technical data ➔ Internet: smt	
	Type of mounting	Switching output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in slot from above, flush with cylinder profile	PNP	Cable, 3-wire	2.5	543 867	SMT-8M-PS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 866	SMT-8M-PS-24V-K-0,3-M8D
			Plug M12x1, 3-pin	0.3	543 869	SMT-8M-PS-24V-K-0,3-M12
		NPN	Cable, 3-wire	2.5	543 870	SMT-8M-NS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 871	SMT-8M-NS-24V-K-0,3-M8D
	Insertable in slot lengthwise, flush with cylinder profile	PNP	Cable, 3-wire	2.5	175 436	SMT-8-PS-K-LED-24-B
			Plug M8x1, 3-pin	0.3	175 484	SMT-8-PS-S-LED-24-B
N/C contact						
	Insertable in slot from above, flush with cylinder profile	PNP	Cable, 3-wire	7.5	543 873	SMT-8M-PO-24V-K7,5-OE

Stopper cylinders DFST

Accessories

FESTO

Ordering data – Proximity sensor for T-slot, magnetic reed					Technical data → Internet: sme	
	Type of mounting	Switching output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in slot from above, flush with cylinder profile	Contacting	Cable, 3-wire	2.5	543 862	SME-8M-DS-24V-K-2,5-OE
				5.0	543 863	SME-8M-DS-24V-K-5,0-OE
			Cable, 2-wire	2.5	543 872	SME-8M-ZS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 861	SME-8M-DS-24V-K-0,3-M8D
	Insertable in slot lengthwise, flush with cylinder profile	Contacting	Cable, 3-wire	2.5	150 855	SME-8-K-LED-24
			Plug M8x1, 3-pin	0.3	150 857	SME-8-S-LED-24
N/C contact						
	Insertable in slot lengthwise, flush with cylinder profile	Contacting	Cable, 3-wire	7.5	160 251	SME-8-O-K-LED-24

Ordering data – Connecting cables				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 333	NEBU-M8G3-K-2.5-LE3
			5	541 334	NEBU-M8G3-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 338	NEBU-M8W3-K-2.5-LE3
			5	541 341	NEBU-M8W3-K-5-LE3