



Cylinders with displacement encoder Product range overview

Function	Туре	Description
Drives	Rodless	
	DDLI	 Without guide With contactless measuring displacement encoder Based on linear drive DGC-K Supply ports on end face System product for handling and assembly technology
	DGCI	 With guide With contactless measuring displacement encoder Based on linear drive DGC Supply ports optionally on end face or front System product for handling and assembly technology
	With piston rod	
	DNCI	 With contactless measuring displacement encoder Various piston rod variants Standards-based cylinder to ISO 15552 DIN VDMA
	DDPC	 With contactless measuring displacement encoder Various piston rod variants Standards-based cylinder to ISO 15552 DIN VDMA
	DNC/DSBC	 With attached potentiometer MLO-LWG Various piston rod variants Standards-based cylinder to ISO 15552 DIN VIDMA
Swivel	Swivel modules	
modules	DSMI	 Based on swivel modules DSM Integrated rotary potentiometer Compact design Wide range of mounting options

Cylinders with displacement encoder Product range overview

Piston \varnothing	Stroke/swivel angle	Suitable								
		for positioning with	for end-position cont		for use as a measuring					
	[mm/°]	CPX-CMAX	CPX-CMPX	SPC11	cylinder					
Rodless				I						
25, 32, 40, 63	100, 160, 225, 300, 360, 450, 500, 600, 750, 850, 1000, 1250, 1500, 1750, 2000	•	•	•	•					
18, 25, 32, 40, 63	100, 160, 225, 300, 360, 450, 500, 600, 750, 850, 1000, 1250, 1500, 1750, 2000		•							
With piston r										
32, 40, 50, 63	10 2000	-	_	_	•					
	100 750	•	•	•	-					
80, 100	10 2000	-	-	-	•					
	100 750	•	•	•						
32, 40, 50, 63, 80	100, 150, 225, 300, 360, 450, 600, 750	•	•	•	•					
Swivel modu	les									
25, 40, 63	270	•	•	•	•					

Features

Servopneumatic drive technology

Positioning and Soft Stop applications as an integral component of the valve terminal CPX – the modular peripheral system for decentralised automation tasks.

The modular design means that valves, digital inputs and outputs, positioning modules and end-position controllers, as appropriate to the application, can be combined in almost any way on the CPX terminal.

Advantages:

- Pneumatics and electrics control and positioning on one platform
- Innovative positioning technology piston rod drives, rodless drives, rotary drives
- Actuation via fieldbus
- Remote maintenance, remote diagnostics, web server, SMS and e-mail alerts are all possible via TCP/IP
- Modules can be quickly exchanged and expanded without altering the wiring

ged the

Axis controller CPX-CMAX



Free choice:

Position and force control, directly actuated or selected from one of 64 configurable position sets. If you are looking for something more: the configurable function for switching to the next set enables simple functional sequences to be realised with the axis controller CPX-CMAX.

All stations are recognised as: the auto-identification function identifies each participant with its device data on the controller CPX-CMAX.

Also included:

The functional scope of the controller CPX-CMAX includes actuation of a brake or clamping unit via the proportional directional control valve VPWP.

Up to 8 modules (max. 8 axes) can be operated in parallel and independently of each other. Commissioning via FCT (Festo configuration software) or via fieldbus: no programming, only configuration.

Technical data → Internet: cpx-cmax

- Advantages:
- Greater flexibility
- OEM friendly commissioning also via fieldbus
- Easy installation and fast commissioning
- Cost-effective
- You program the system in your PLC environment

Features

End-position controller CPX-CMPX



Fast travel between the mechanical end stops of the cylinder, stopping gently and without impact in the end position.

Fast commissioning via control panel, fieldbus or handheld unit. Improved control of downtime. Actuation of a brake or clamping unit via the proportional directional control valve VPWP is an integral part of the controller CMPX. Depending on the fieldbus chosen, up to 9 end-position controllers can be actuated on the CPX terminal. All system data can be read and written via the fieldbus, including, for example, the mid positions. Technical data → Internet: cpx-cmpx

FESTO

Advantages:

- Greater flexibility
- OEM friendly commissioning also via fieldbus
- Easy installation and fast commissioning
- Cost-effective
- up to 30% faster cycle rates
 significantly reduced system vibration
- Improved work ergonomics thanks to significantly reduced noise level
- The extended diagnostics help to reduce the service time of the machine

Technical data → Internet: vpwp

Advantages:

- Easy installation and fast commissioning
- Reduction of system downtimes thanks to the new diagnostic options
- With switching output for actuating a brake/clamping unit

Proportional directional control valve VPWP



The 5/3-way proportional directional control valve for applications with Soft Stop and pneumatic positioning. Fully digitalised – with integrated pressure sensors, with new diagnostic functions. In sizes 4, 6, 8 and 10. Flow rate of 350, 700, 1400 and 2000 l/min. With switching output for actuating a brake. Coloured supply ports.

Pre-assembled cables guarantee faultless and fast connection with the controllers CPX-CMPX and CPX-CMAX.

Measuring module CPX-CMIX




Fully digital data acquisition and transmission means that pneumatic cylinders can be used as sensors. With very high repetition accuracy and incorporating both analogue and digital measuring sensors. Suitable for the linear drive DGCI with displacement encoder for measuring absolute values, for the piston rod drive DNCI/DDPC with incremental displacement encoder or even for a potentiometer of the type MLO.

Technical data → Internet: cpx-cmix

Advantages: • All process steps can be docu-

- mented, which improves quality
- An adjustable contact force (via pressure regulator) increases the precision of the "displacement sensor"
- With displacement encoders for measuring absolute values, the actual position is immediately available after the system is switched on

Drive options



Drive options

System with swivel module DSMI 6 7 4 1 Controller module CPX-CMPX or CPX-CMAX 2 Proportional directional control valve VPWP 3 Swivel module DSMI with displacement encoder

- 4 Sensor interface CASM-S-D2-R3
- 6 Connecting cable KVI-CP-3-...
- 7 Connecting cable NEBC-P1W4-K-0,3-N-M12G5

System with potentiometer

7 6 4 8

- 1 Controller module CPX-CMPX or CPX-CMAX
- 2 Proportional directional control valve VPWP
- 4 Sensor interface CASM-S-D2-R3
- 6 Connecting cable KVI-CP-3-...
- 7 Connecting cable NEBC-P1W4-K-0,3-N-M12G5
- 8 Connecting cable NEBC-A1W3-K-0,4-N-M12G5

- Swivel module DSMI with integrated displacement encoder
- Identical design to pneumatic swivel module DSM
- Absolute displacement encoder based on a potentiometer
- Swivel range of 0 ... 270°
- Size: 25, 40, 63
- Max. torque: 5 ... 40 Nm • Range of applications: Soft Stop and pneumatic positioning
- Mass moments of inertia from 15 ... 6000 kgcm² and a matching sensor interface CASM-S-D2-R3
- Pre-assembled cables guarantee faultless and fast connection with the proportional directional control valve VPWP

Technical data → Internet: dsmi

Advantages:

- Complete drive unit, compact, can be used immediately
- High angular acceleration
- With adjustable fixed stops • For fast and accurate positioning
- down to ±0.2° (only with axis controller CPX-CMAX)

• Attachable potentiometers with absolute measurement, with high degree of protection

- With connecting rod or moment compensator
- Measuring range: Connecting rod: 100 ... 750 mm Moment compensator: 225 ... 2000 mm
- Pre-assembled cables guarantee faultless and fast connection with the sensor interface CASM
- Range of applications: Soft Stop and pneumatic positioning with cylinder \emptyset 25 ... 80 mm, e.g. DNC or DSBC
- Loads from 1 ... 300 kg

Technical data → Internet: casm

Advantages:

- Easy installation and fast commissioning
- Cost-effective
- Can also be used in harsh ambient conditions
- Variety of drives: CPX-CMPX and CPX-CMAX also support cylinders with external displacement encoder



Cylinders with displacement encoder Drive options

System components for Soft Sto	op systems with en	d-position controller CPX-	СМРХ			
	Linear drive	Standard cylinder	Swivel module	Displacement encod	ler	→ Page/
	DDLI/DGCI	DNCI, DDPC	DSMI	MLO-LWG/-TLF	MME-MTS	Internet
End-position controller						
CPX-CMPX	-		-	-	-	стрх
Prop. directional control valve					_	
VPWP			-	-	•	vpwp
Sensor interface						
CASM-S-D2-R3	_	-	-	-	_	casm
Sensor interface			_			cocm
CASM-S-D3-R7	-	-	-	-	-	casm
Connecting cable						kvi
KVI-CP-3	-	-	-	-	-	KVI
Connecting cable				- /		naha
NEBC-P1W4	-	-	-	■ / -	-	nebc
Connecting cable				-/		nebc
NEBC-A1W3	-	_	_	-/-	-	nebc
Connecting cable						VDWD
NEBP-M16W6	-	-	_	-	-	vpwp

	Linear drive	Linear drive Standard cylinder Swivel module Displacement encoder		der	→ Page/	
	DDLI/DGCI	DNCI, DDPC	DSMI	MLO-LWG/-TLF	MME-MTS	Internet
Axis controller	_		_	_		emey
CPX-CMAX		-	-	-	-	cmax
Prop. directional control valve						
VPWP		-	-	-	-	vpwp
Sensor interface						carm
CASM-S-D2-R3	-	-	-	-	-	casm
Sensor interface						casm
CASM-S-D3-R7	-	-	_	_	_	Casili
Connecting cable						kvi
KVI-CP-3	-	-	-	-	-	KVI
Connecting cable				■ / -		nebc
NEBC-P1W4	-	-	-	■ / -	-	nebc
Connecting cable	_	_	_	- / ■	_	nebc
NEBC-A1W3	_	-	_	-/-	_	nebc
Connecting cable	_		_	_		VDWD
NEBP-M16W6	-	-	-	-	-	vpwp


System components for measuring cylinders with measuring module CPX-CMIX

	Linear drive	Standard cylinder	Swivel module	Displacement encode	er	→ Page/			
	DDLI/DGCI	DNCI, DDPC	DSMI	MLO-LWG/-TLF	MME-MTS	Internet			
Measuring module	_			_		cmiv			
CPX-CMIX-M1-1	-	-	-	-	-	cmix			
Sensor interface						cocm			
CASM-S-D2-R3	_	-	-	-	_	casm			
Sensor interface						casm			
CASM-S-D3-R7	_	-				Casili			
Connecting cable	(■)1)				(■)	kvi			
KVI-CP-3	(=)-/	-	-	-	(=)	KVI			
Connecting cable				■ / -		nebc			
NEBC-P1W4	_	_	-	- / -	_	nenc			
Connecting cable	_	_	_	-/	_	nebc			
NEBC-A1W3	_	_	_	-/-	_	HEDC			
Connecting cable	_	_	_	_		VDWD			
NEBP-M16W6	-	_	_	-	-	vpwp			

1) As an extension


FESTO

Overview



Standard cylinders DDPC, integrated displacement encoder Peripherals overview

FESTO



-Note -

If the drive DDPC is used without an end-position controller CPX-CMPX, SPC11 or axis controller CPX-CMAX, e.g. as a measuring cylinder, then the standard accessories for the drive DNC can be used.

Standard cylinders DDPC, integrated displacement encoder Peripherals overview



.

Acce	ssories		
	Туре	Description	→ Page/Internet
1	Rod eye	With spherical bearing	22
	SGS		
2	Foot mounting	For mounting the drive on the bearing and end cap	22
	HNC		
3	Flange mounting	For mounting the drive on the bearing and end cap	22
	FNC		
4	Guide unit ¹⁾	For protecting against rotation at high torque loads	20
	FENG-KF		
5	Trunnion support	For securing the trunnion mounting kit DAMT	24
	LNZG		
6	Trunnion mounting kit	For swivelling movements of the drive	23
	DAMT		
7	Slot cover	For protecting against the ingress of dirt	24
	ABP-5-S		
8	Proximity sensor	For additional sensing of the piston position, can be ordered optionally, only in combination	sm
	SME/SMT-8	with the order code A in the modular products section for the drive	
9	Sensor interface	Used to connect pneumatic drives with analogue/incremental displacement encoder to a	casm
	CASM	position controller CPX-CMAX or CPX-CMPX	
10	Push-in fitting	For connecting compressed air tubing with standard O.D.	24
	QS		

1) Guide unit FENG-KF must be attached to the piston rod in a way that eliminates backlash



Allocation table of drives and associated proportional directional control valves \rightarrow page 25

	DD	PC 1	- Q] -]]-[] - [] - [- P)	A	-
Туре												
DDPC	Standard cylinder											
	1											
	on against rotation											
Q	With protection against rotation			_								
Piston Ø	ð [mm]											
					J							
Stroke	mm]											
Guide u	nit											
-	None											
D	Attached											
Clampir	ıg unit											
-	None											
С	Attached											
Piston r	od type											
-	At one end											
Т	Through piston rod											
1												
Cushior												
Р	Elastic cushioning rings/pads at both ends											
Position	i sensing											
А	Via proximity sensor											
Distor r	od extension	_										
	None											
- E	None 1 500 mm	-										
C	1 500 mm											

Technical data



General technical data

General technical data									
Piston \varnothing		80	80 100						
Based on standard		ISO 15552							
Design		Piston							
		Piston rod							
		Profile barrel							
Mode of operation		Double-acting							
Guide ¹⁾	Guide rod with yoke, with ball bearing	g guide							
Protection against rotation	Square piston rod								
Mounting position	Any								
Type of mounting	Via accessories								
Cushioning		Elastic cushioning rings/pads at both ends							
Position sensing		Integrated displacement encoder							
		Via proximity sensor ²⁾							
Measuring principle (displacement encoder)		Encoder, non-contacting and relative measurement							
Pneumatic connection	G3/8		G1/2						
Stroke									
DDPC ³⁾	10 2000								
DDPCD	[mm]	100 500							
Extended piston rod	[mm]	1 500							

1) Guide unit FENG-KF can be ordered via the modular product system (feature D) and is supplied attached. The maximum stroke is restricted.

2) Not included in the scope of delivery, can be ordered as an option

3) Can only be used without restriction as a positioning drive in the range from 100 ... 750 mm. Note stroke reduction in combination with CPX-CMAX

Operating and environmental conditions							
Operating pressure	[bar]	4 12					
Operating pressure ¹⁾	[bar]	48					
Operating medium ²⁾		Compressed air to ISO 8573-1:2010 [6:4:4]					
Note on operating/pilot medium		Operation with lubricated medium not possible					
		Pressure dew point 10 °C below ambient/medium temperature					
Ambient temperature ³⁾	[°C]	-20 +80					
Vibration resistance to DIN/IEC 68 Part 2-6		Severity level 2					
Continuous shock resistance to DIN/IEC 68 I	Part 2-82	Severity level 2					
CE mark (see declaration of conformity) ⁴⁾		To EU EMC Directive					
Corrosion resistance class CRC ⁵⁾		1					

1) Only applies to applications with end-position controller CPX-CMPX, SPC11 and axis controller CPX-CMAX

Characteristic values contingent on the proportional directional control valve VPWP, MPYE
 Note operating range of proximity sensors

4) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com/sp -> Certificates.

If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary. 5) Corrosion resistance class CRC 1 to Festo standard FN 940070


Low corrosion stress. For dry indoor applications or transport and storage protection. Also applies to parts behind covers, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions).

Technical data

Forces [N] and impact energy [Nm]								
Piston Ø	80	100						
Theoretical force at 6 bar, advancing	3016	4712						
Theoretical force at 6 bar, retracting	2721	4418						
Impact energy at the end positions	1.8	2.5						

Permissible impact velocity:

V	_ 2 x E _{perm.}
Vperm.	$=\sqrt{\frac{1}{m_{dead}} + m_{load}}$
	2 v F



Note

These specifications represent the maximum values that can be achieved. Note the maximum permissible impact energy.

Maximum permissible load:

 $m_{load} = \frac{2 \times E_{perm.}}{m_{load}} - m_{dead}$ v²

Positioning characteristics with axis controller CPX-CMAX

Piston Ø		80	100	
Stroke	[mm]	100 750		
Mounting position		Any		
Resolution	[mm]	0.01		
Repetition accuracy	[mm]	≤ ±0.5		
Min. load, horizontal	[kg]	20	32	
Max. load, horizontal	[kg]	300	450	
Min. load, vertical ¹⁾	[kg]	20	32	
Max. load, vertical ¹⁾	[kg]	100	150	
Min. travel speed	[m/s]	0.05		
Max. travel speed	[m/s]	1	0.7	
Typical positioning time, long stroke ²⁾	[s]	0.88/1.02	0.95/1.10	
Typical positioning time, short stroke ³⁾	[s]	0.77/0.95	0.80/1.32	
Min. positioning stroke ⁴⁾	[%]	≤ 3		
Stroke reduction ⁵⁾ [mm]		15		
Recommended proportional directional con	ntrol valve	- ·		
For CPX-CMAX		→ page 25		

1) Only in combination with external guide

2)

At 6 bar, horizontal mounting position, DDPC-XX-500, 400 mm positioning travel at min./max. load At 6 bar, horizontal mounting position, DDPC-XX-500, 200 mm positioning travel at min./max. load 3)

4) Refers to the cylinder stroke, but not more than 10 mm

5) The stroke reduction must be maintained on each side of the drive, the max. positionable stroke is therefore: stroke - 2x stroke reduction

Force control characteristics with axis controller CPX-CMAX										
Piston Ø		80	100							
Stroke	[mm]	100 750								
Mounting position		Any								
Max. controllable force ¹⁾	[N]	2710/2440	4240/3975							
Typical friction forces ²⁾	[N]	140	160							
Repetition accuracy	[%]	<±2								
pressure regulation ³⁾⁴⁾										

1) Advancing/retracting at 6 bar

These values can fluctuate greatly from cylinder to cylinder and are not guaranteed. 2)

These friction forces must also be taken into consideration when using an external guide or when the cylinder is moving other components subject to friction

This value defines the repetition accuracy with which the internal differential pressure in the cylinder is controlled and refers to the maximum controllable force (the internal differential pressure corresponds to the 3) prescribed force setpoint value)

4) The effective force at the workpiece and its accuracy depends largely on the friction in the system as well as the repetition accuracy of the internal control system. Note that friction forces always work against the direction of movement of the piston. The following formula can be used as a rule of thumb for the force F at the workpiece: $F = F_{setpoint} \pm F_{friction forces} \pm internal repetition accuracy$

Standard cylinders DDPC, integrated displacement encoder Technical data

Positioning characteristics with S	Positioning characteristics with Soft Stop end-position controller CPX-CMPX, SPC11									
Piston \varnothing		80	100							
Stroke	[mm]	100 750								
Mounting position		Any								
Repetition accuracy	[mm]	±2								
Min. load, horizontal	[kg]	20	32							
Max. load, horizontal	[kg]	300	450							
Min. load, vertical ¹⁾	[kg]	20	32							
Max. load, vertical ¹⁾	[kg]	100	150							
Travel time	[s]	➔ Soft Stop sizing software:	→ www.festo.com							
Recommended proportional direct	ional control valve									
For CPX-CMPX		→ page 25								
For SPC11	SPC11 → page 25									

1) Only in combination with external guide

Electrical data – Displacement encoder		
Output signal		Analogue
Independent linearity		·
Strokes up to 500 mm	[mm]	< ±0.08
Strokes up to 1000 mm	[mm]	< ±0.09
Strokes above 1000 mm	[mm]	<±0.11
Max. travel speed	[m/s]	1.5
Protection class		IP65
CE marking (see declaration of conformity)		In accordance with EU EMC Directive ¹⁾
Max. permitted magnetic disruption field ²⁾	[kA/m]	10
Electrical connection		Cable with 8-pin plug, round type M12
Cable length	[m]	1.5

For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com/sp → Certificates. If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.
 At 100 mm interval

Pin assignment of plug



Pin	Function	Colour
1	5 V	Black
2	GND	Brown
3	sin+	Red
4	sin-	Orange
5	COS-	Green
6	COS+	Yellow
7	Screening	Screened
8	n.c.	-


Standard cylinders DDPC, integrated displacement encoder Technical data

FESTO

.

Weight [g]									
Piston Ø	80	100							
DDPC									
Basic weight with 0 mm stroke30534330									
Additional weight per 10 mm stroke	87	95							
Moving load with 0 mm stroke	804	994							
Additional weight per 10 mm stroke	31	31							
DDPCT – Through piston rod									
Basic weight with 0 mm stroke	3537	5019							
Additional weight per 10 mm stroke	127	134							
Moving load with 0 mm stroke	1247	1467							
Additional weight per 10 mm stroke	70	70							
DDPCE – Additional weight with piston rod external	ension								
Additional weight per 10 mm extension	31	31							
DDPCC – Additional weight with clamping unit									
Additional weight	2046	2829							
DDPCD – Additional weight with guide unit									
Basic weight with 0 mm stroke	10430	12990							
Additional weight per 10 mm stroke	80	80							

Materials




Standard cylinder							
1 End cap	Wrought aluminium alloy						
2 Piston rod	High-alloy steel						
3 Cylinder barrel	Wrought aluminium alloy						
– Seals	NBR, polyurethane						
Note on materials	Free of copper and PTFE						
	RoHS-compliant						

Technical data

Torques and lateral forces

Max. torque for protection against rotation Dynamic ≤ 3 Nm ≤ 5 Nm Static An external guide unit FENG-KF is recommended with higher torque loads. The guide unit is supplied attached.

The permissible static and dynamic characteristic load values with and without attached guide → Internet: feng




Mounting conditions

When mounting a drive A with magnet (for position sensing) next to a standard cylinder DDPC, the following conditions must be observed:

- Х Minimum distance between the drives
- Y Offset between the drives on the bearing cap


Parallel assembly

If the offset Y = 0 mm, the drives can be assembled directly next to one another.




Offset assembly, cable outlet between the drives

If the offset is Y > 0 mm and the cable outlet is between the drives, a distance of X > 70 mm must be observed.




Offset assembly, cable outlet upwards or downwards

If the offset is Y > 0 mm and the cable outlet is up or down, a distance of X > 60 mm must be observed.




FESTO


Technical data




Standard cylinders DDPC, integrated displacement encoder Technical data



DDPC-...-CT – Through piston rod with clamping unit



DDPC-...-E – Extended piston rod




Ø	A2	D1	D2	H1	L3	L5
		Ø				
[mm]	max.	f9				
80	500	48	G1/8	165.5	95	31.5
100	500	48	G1/8	174	98	31

Ø	VD	WH	2	[]	ZM			
[mm]			DDPCT	DDPCCT	DDPCT	DDPCCT		
80	16.7	46	174	269	222	317		
100	20.5	51	189	287	240	338		



Technical data




Standard cylinders DDPC, integrated displacement encoder Ordering data – Modular products

Or	dering table						
Pis	Piston Ø		80 100		Condi- tions	Code	Enter code
Μ	Module No.		1677705	1691433			
	Function		Standard cylinder with integrated displa	cement encoder		DDPC	DDPC
	Protection against rotation		With protection against rotation			-Q	-Q
	Piston \varnothing	[mm]	80	100			
	Stroke	[mm]	10 2000		1		
0	Guide unit		None				
			Attached			-D	
	Clamping unit		None				
			Attached		2	-C	
	Piston rod type		At one end				
			Through piston rod			Т	
Μ	Cushioning Elastic cushioning rings/pads at both ends					-P	-P
	Position sensing		Via proximity sensor		Α	A	
0	Piston rod extension		None				
		[mm]	1 500			E	

1 -... Can only be used without restriction as a positioning drive in the range from 100 ... 750 mm

2 C Only available with T






Accessories

Foot mounting HNC

Materials: Galvanised steel Free of copper and PTFE





Dimensions a	and ordering data								
For \varnothing	AB	AH	AO	AT	AU	SA			
	Ø								
[mm]						DDPC	DDPCC		
80	12	63	15	6	41	276	371		
100	14.5	71	17.5	6	41	220	318		

For \varnothing	TR	US	ХА		XS	CRC ¹⁾	Weight	Part No.	Туре
[mm]			DDPC	DDPCC			[g]		
80	63	93	281	376	81	2	829	174373	HNC-80
100	75	110	230	328	86	2	1009	174374	HNC-100


1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

Flange mounting FNC

Materials: FNC: Galvanised steel Free of copper and PTFE RoHS-compliant





Dimensions and ordering data

Dimensions	ina oraci												
For \varnothing	E	FB	MF	R	TF	UF	W	Z	F	CRC ¹⁾	Weight	Part No.	Туре
		Ø						DDPC	DDPCC				
[mm]		H13									[g]		
80	93	12	16	63	126	150	30	256	351	1	1495	174380	FNC-80
100	110	14	16	75	150	175	35	205	303	1	2041	174381	FNC-100

1) Corrosion resistance class CRC 1 to Festo standard FN 940070

Low corrosion stress. For dry indoor applications or transport and storage protection. Also applies to parts behind covers, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions).


FESTO


Accessories

Rod eye SGS

Scope of delivery: 1 rod eye, 1 hex nut to DIN 439

Materials: Galvanised steel RoHS-compliant





Dimensions and ordering data

Dimensions															
For Ø	AV	B1	CE	CN	D1	EF	EN	EU	Z	=©1	=©2	CRC ^{1) 2)}	Weight	Part No.	Туре
				Ø	Ø										
[mm]				H7		±0.5			[°]				[g]		
M20x1.5	33 -2	10	77	20	34	25	25	18	15	30	30	1	464	9264	SGS-M20x1,5

1) Corrosion resistance class CRC 1 to Festo standard FN 940070

Low corrosion stress. For dry indoor applications or transport and storage protection. Also applies to parts behind covers, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions).

The following applies for the ball: 2)

Corrosion resistance class CRC 0 to Festo standard FN 940070


No corrosion stress. Applies to small, optically irrelevant standard parts such as threaded pins, circlips and clamping sleeves which are usually only available in a phosphated or burnished version (and possibly oiled) as well as to ball bearings (for components < CRC 3) and plain bearings.

Trunnion mounting kit DAMT

The mounting kit can be attached at any position along the profile barrel of the cylinder.

Materials: Galvanised steel Free of copper and PTFE RoHS-compliant





Dimensions and ordering data For Ø Β1 C2 С3 TD TL ΤM UW XG Ø DDPC-... DDPC-...-C e9 [mm] 80 20 206 44 136 156 20 110 130 111 100 48 189 25 25 132 145 123 221 164

For \varnothing	XJ		XV		Max. tightening torque	CRC ¹⁾	Weight	Part No.	Туре
	DDPC	DDPCC	DDPC	DDPCC					
[mm]					[Nm]		[g]		
80	175	270	143	238	28+2	1	1494	163529	DAMT-V1-80-A
100	117	215	120	218	28+2	1	2095	163530	DAMT-V1-100-A

1) Corrosion resistance class CRC 1 to Festo standard FN 940070


Low corrosion stress. For dry indoor applications or transport and storage protection. Also applies to parts behind covers, in the non-visible interior area, and parts which are covered in the application (e.g. drive trunnions).

Accessories

Trunnion support LNZG

Materials: Trunnion support: Anodised aluminium Plain bearing: Plastic Free of copper and PTFE RoHS-compliant





Dimensions a	Dimensions and ordering data														
For \varnothing	CR	DA	FK	FN	FS	H1	HB	KE	NH	TH	UL	CRC ¹⁾	Weight	Part No.	Туре
	Ø	Ø	Ø				Ø								
[mm]	D11	H13	±0.1				H13			±0.2			[g]		
80	20	18	20	40	13	20	11	11	23	42	65	2	178	32961	LNZG-63/80
100	25	20	25	50	16	24.5	14	13	28.5	50	75	2	306	32962	LNZG-100/125

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

Ordering data

olucinguata									
	For \varnothing	Comment	Part No.	Туре	PU ¹⁾				
Slot cover Technical data 🗲 Internet: abj									
	80, 100	Every 0.5 m	151680	ABP-5-S	2				

1) Packaging unit

1

Accessories

Ordering data – Proportional d	irectional cont	rol valves and push	n-in fittings					
	For \varnothing	Stroke	Proportion	al directional control valve	Push-in fit	Push-in fitting for DDPC		
			Technical d	lata 🗲 Internet: vpwp	Technical			
	[mm]	[mm]	Part No.	Туре	Part No.	Туре	PU ¹⁾	
	For applica	tions with axis cont	roller CPX-CMA	X				
	80	100 200	550171	VPWP-6-L-5-Q8-10-E	186100	QS-G3/8-8	10	
		201 450	550172	VPWP-8-L-5-Q10-10-E	186102	QS-G3/8-10		
		451 750	1552544	VPWP-10-L-5-Q-10-E-G-EX1	186103	QS-G3/8-12		
	100	100 120	550171	VPWP-6-L-5-Q8-10-E	186104	QS-G1/2-12 ²⁾	1	
OP SOO		121 330	550172	VPWP-8-L-5-Q10-10-E	186104	QS-G1/2-12 ³⁾		
00		331 750	1552544	VPWP-10-L-5-Q-10-E-G-EX1	186104	QS-G1/2-12		

Ordoring data rtional directional c

Packaging unit
 With additional reduction from Ø 12 to Ø 8, with push-in connector QS-12H-8 (part number 130624)

With additional reduction from Ø 12 to Ø 10, with push-in connector QS-12H-10 (part number 153044)

Ordering data - Proportional directional control valves and push-in fittings

· ,	For Ø	Stroke	Droportiona	I directional control valve	Duch in fitt	ing for DDDC		
					Push-in fitting for DDPC			
			Technical da	ata 🗲 Internet: vpwp	Technical data 🗲 Internet: qs			
	[mm]	[mm]	Part No.	Туре	Part No.	Туре	PU ¹⁾	
	For application	ns with Soft Stop en	d-position co	ntroller CPX-CMPX				
	80	100 125	550170	VPWP-4-L-5-Q8-10-E	186100	QS-G3/8-8	10	
		126 160	550171	VPWP-6-L-5-Q8-10-E	186100	QS-G3/8-8		
		161 400	550172	VPWP-8-L-5-Q10-10-E	186102	QS-G3/8-10		
		401 500	1552544	VPWP-10-L-5-Q-10-E-G-EX1	186103	QS-G3/8-12		
R C F COCE	100	100 150	550171	VPWP-6-L-5-Q8-10-E	186104	QS-G1/2-12 ²⁾	1	
		151 350	550172	VPWP-8-L-5-Q10-10-E	186104	QS-G1/2-12 ³⁾		
`		351 500	1552544	VPWP-10-L-5-Q-10-E-G-EX1	186104	QS-G1/2-12		

1) Packaging unit

With additional reduction from Ø 12 to Ø 8, with push-in connector QS-12H-8 (part number 130624)
 With additional reduction from Ø 12 to Ø 10, with push-in connector QS-12H-10 (part number 153044)

Ordering data – Proportional directional control valves and push-in fittings

oracing auta rioportions	at an ecclonat con	not raties and past						
	For Ø	Stroke	Proportion	Push-in fit	Push-in fitting for DDPC			
			Technical d	ata 🗲 Internet: mpye	Technical			
	[mm]	[mm]	Part No.	Туре	Part No.	Туре	PU ¹⁾	
\frown	For applica	tions with Soft Stop	end-position c	ontroller SPC11				
	80	100 125	151692	MPYE-5-1/8-LF-010-B	186100	QS-G3/8-8	10	
		126 160	151693	MPYE-5-1/8-HF-010-B	186100	QS-G3/8-8		
		161 400	151694	MPYE-5-1/4-010-B	186102	QS-G3/8-10		
No. L		401 500	151695	MPYE-5-3/8-010-B	186103	QS-G3/8-12		
	100	100 150	151693	MPYE-5-1/8-HF-010-B	186104	QS-G1/2-12 ²⁾	1	
		151 350	151694	MPYE-5-1/4-010-B	186104	QS-G1/2-12 ³⁾		
		351 500	151695	MPYE-5-3/8-010-B	186104	QS-G1/2-12		

1) Packaging unit

With additional reduction from \varnothing 12 to \varnothing 8, with push-in connector QS-12H-8 (part number 130624) 2)

3) With additional reduction from \varnothing 12 to \varnothing 10, with push-in connector QS-12H-10 (part number 153044)

