Spindle axis units ELGS-BS-KF

FESTO





Key features

At a glance

Plug and work with the Simplified Motion Series



The simplicity of pneumatics is now combined for the first time with the advantages of electric automation thanks to the Simplified Motion Series. These integrated drives are the perfect solution for all users who are looking for an electric alternative for very simple movement and positioning tasks between two mechanical end positions, but don't want the commissioning process for traditional electric drive systems that can often be quite complex.

Integrated

The integrated electronics in the drive are at the core of the Simplified Motion Series.

Simple

For commissioning, simply set all relevant parameters directly on the drive:

- · Speed and force
- Reference end position and cushioning
- Manual operation

IO-Link

There is no need for any software since operation is simply based on the "plug and work" principle. Digital I/O (DIO) and IO-Link are always automatically included – a product with two types of control as standard.

Standardised

Electrical connection via

M12 plug design

- Power (4-pin): power supply for the motor
- Logic (8-pin): control signal, sensor signal and power for the integrated electronics


Connected

Use of extended functions via IO-Link:

- Motion parameters can be set remotely
- Copy and backup function for transferring parameters
- Read function for extended process parameters


The functions of the Simplified Motion Series

Basic profile for movement between two end positions: with speed control



- These drives are designed for simple movements between two end positions.
- Proximity switches are required in order to implement any intermediate positions.

Extended motion profile for simplified press-fitting and clamping functions: with speed and force control



The products in the Simplified Motion Series

Spindle axis unit ELGS-BS-KF



Toothed belt axis unit ELGS-TB-KF



Mini slide unit EGSS-BS-KF



Toothed belt axis unit



→ Internet: www.festo.com/catalogue/...

Electric cylinder unit




Rotary drive unit



Key features

At a glance



- Without external servo drive: all the necessary electronic components are combined in the integrated drive
- Two control options integrated as standard: digital I/O and IO-Link
- Complete solution for simple movements between two mechanical end positions
- Protected against external influences by internal guide
- Simplified commissioning: all parameters can be manually set directly on the drive
- No special expertise required for commissioning
- End position feedback similar to that of a conventional proximity switch is integrated as standard
- Clean Look design: easy to clean and less prone to contamination

Modular and flexible with motor, motor mounting kit and servo drive

This product is also available as a modular mechanical system as spindle axis ELGC-BS-KF:




When to compact dimensions and optimised installation space are important, e.g. in assembly systems, test and inspection systems, small parts handling, the electronics industry and desktop applications. Either as an individual axis or as a handling system.

- Compact: optimum ratio of installation space to working space
- Unique: "one-size-down" mounting system
- Modular: individual combinations with motor, motor mounting kit and servo drive
- Flexible: wide range of mounting options for optimum machine integration


Typical handling systems

For applications where compact dimensions are essential, the axes ELGC can be combined into very space-saving handling systems that are suitable for assembly systems, test and inspection systems, small parts handling, the electronics industry and desktop applications. The very compact linear axes ELGC, mini slide EGSC and electric cylinder EPCC offer an optimal ratio between installation space and working space. They feature a common system approach and platform architecture and the connections are largely adapterless.






Planar surface gantry



Three-dimensional gantry




Key features


Matrix showing combinations between axis ELGC/ELGS-TB, ELGC/ELGS-BS, mini slide EGSC/EGSS-BS, electric cylinder EPCC/EPCS-BS and guide axis ELFC Mounting options with profile mounting and via angle kit


		Assembly axis ELGC-BS/-TB; ELFC; EGSC-BS; EPCC-BS; ELGS-BS/-TB; EGSS-BS, EPCS-BS				
	Size	25	32	45	60	
Base axis	32	•	-	-	-	
ELGC-BS/-TB; ELFC;	45	-	•	-	-	
ELGS-BS/-TB	60	-	-		-	
	80	-	-	-	•	

With profile mounting EAHF-L2-...-P-D...



• Mounting option: base axis with one-size-down assembly axis






With angle kit EHAA-D-L2-...-AP



 Mounting option: base axis rotated through 90° with one-size-down assembly axis






Matrix showing combinations between axis ELGC/ELGS-TB, ELGC/ELGS-BS, mini slide EGSC/EGSS-BS, electric cylinder EPCC/EPCS-BS and guide axis ELFC Assembly options with adapter kit or direct mounting


			axis ELGC-I TB; EGSS-B			; EPCC-BS;
	Size	25	32	45	60	80
Base axis	32		•	-	-	_
ELGC-BS/-TB; ELFC;	45	-			-	-
ELGS-BS/-TB	60	-	-			_
	80	-	-	-		•


			Assembly axis EGSC-BS; EGSS-BS			
	Size	25	32	45	60	
Base axis	25	•	-	-	-	
EGSC-BS;	32	-	•	-	-	
EGSS-BS	45	-	-	•	-	
	60	_	-	-	•	

With adapter kit EHAA-D-L2

- Mounting option: base axis with the same size assembly axis
- Mounting option: base axis with height adjustment for one-size-down assembly axis
- When motors are mounted using parallel kits, this may lead to interfering contours. In this case, the adapter plate is required for height compensation







With direct mounting

Mounting option: base axis with the same size assembly axis





Type codes

001	Series	
ELGS	Gantry axis	
002	Drive system	
BS	Ball screw drive	
	Data Sciew drive	
003	Guide	
KF	Recirculating ball bearing guide	
004	Size	
32	32	
45	45	
60	60	
005	Stroke	
100	100	
100	100 200	
200	200	
200 300	200 300	
200 300 400 500 600	200 300 400 500 600	
200 300 400 500	200 300 400 500	
200 300 400 500 600	200 300 400 500 600	
200 300 400 500 600 800	200 300 400 500 600 800	
200 300 400 500 600 800 006 8P	200 300 400 500 600 800 Spindle pitch 8 mm 10 mm	
200 300 400 500 600 800	200 300 400 500 600 800 Spindle pitch 8 mm	
200 300 400 500 600 800 006 8P	200 300 400 500 600 800 Spindle pitch 8 mm 10 mm	

800	Controller	
M	Integrated	
009	Control panel	
H1	Integrated	
010	Bus protocol/activation	
PLK	PNP and IO-Link®	
NLK	NPN and IO-Link®	
011	End-position sensing	
AA	With integrated end-position sensing	
012	Cable outlet direction	
	Standard	
D	Underneath	
D F	Underneath Front	
	1	
F	Front	
F B	Front Rear	
F B	Front Rear Electrical accessories	
F B 013	Front Rear Electrical accessories None	
F B 013	Front Rear Electrical accessories None Adapter for operation as IO-Link® device	

Peripherals overview







[1] Pushbutton actuators for parameterisation and control

Peripherals overview


	Type/order code	Description	→ Page/Internet
[1]	Centring pin/sleeve ZBS, ZBH	For centring loads and attachments on the slide	30
[2]	Adapter kit EHAA-D-L2	 For axis/axis mounting with adapter plate Mounting option: base axis with the same size or one-size-down assembly axis When motors are mounted using parallel kits, this may lead to interfering contours. In this case, the adapter plate is required for height compensation (download CAD data → www.festo.com) 	27
[3]	Profile mounting EAHF-L2P-D	For axis/axis mounting without adapter plate Mounting option: base axis with one-size-down assembly axis	26
[4]	Angle kit EHAA-D-L2AP	For mounting one-size-down vertical axes (assembly axes) on base axes with mounting position "slide at top"	28
[5]	Clamping component EADT-S-L5-32	Tool for retensioning the cover strip	30
[6]	Sensor bracket ¹⁾ EAPM-L2-SH	For mounting the proximity switches on the axis. The proximity switches can only be mounted using the sensor bracket	29
[7]	Proximity switch ¹⁾ SIES-8M	Inductive proximity switch, for T-slot	30
	Proximity switch ¹⁾ SMT-8M	Magnetic proximity switch, for T-slot	30
[8]	Switch lug ¹⁾ EAPMSLS	For sensing the slide position in conjunction with inductive proximity switches SIES-8M	29
[9]	Profile mounting EAHF-L2P	For mounting the axis on the side of the profile. The profile mounting can be attached to the mounting surface using the drill hole in the centre	25
[10]	Profile mounting EAHF-L2	For mounting the axis on the side of the profile	24
11]	Supply cable NEBL-T12	For connecting load and logic supply	31
12]	Connecting cable NEBC-M12	For connection to a controller	31
13]	Adapter NEFC-M12G8	Connection between the motor and the and IO-Link master	31
[14]	IO-Link master USB CDSU-1	For straightforward use of the mini slide unit via IO-Link	31

¹⁾ Proximity switches are optional and only required in order to sense any intermediate positions.



Size 32 ... 60

- Stroke length 100 ... 800 mm



General technical data						
Size		32	45	60		
Design		Electromechanical axis with ball screw a	and integrated drive			
Motor type		Stepper motor				
Guide		Recirculating ball bearing guide				
Mounting position		Any				
Working stroke	[mm]	100, 200, 300, 400, 500, 600, 800	100, 200, 300, 400, 500, 600, 800	100, 200, 300, 400, 500, 600, 800		
Stroke reserve	[mm]	0				
Additional functions		Integrated end-position sensing				
		User interface				
Display		LED				
Homing		Positive fixed stop block				
		Negative fixed stop block				
Type of mounting		With female thread				
		With accessories				
		With centring pin, centring sleeve				
Max. line length						
Inputs/outputs	[m]	15				
IO-Link operation	[m]	20				

Mechanical data					
Size		32	45	60	
Max. payload					
Horizontal	[kg]	2	10	20	
Vertical	[kg]	2	5	13	
Max. feed force F _x	[N]	40	100	200	
Max. speed ¹⁾	[m/s]	0.18	0.25	0.25	
Max. acceleration	[m/s ²]	5			
Repetition accuracy	[mm]	±0.015	±0.015	±0.01	
Reversing backlash	[mm]	≤ 0.15			
Position sensing		For proximity switch			
		Via IO-Link			

¹⁾ Rotational speed and speed are stroke-dependent

Spindle					
Size		32	45	60	
Diameter	[mm]	8	10	12	,
Pitch	[mm/rev.]	8	10	12	
Electrical data					
Size		32	45	60	
Motor			:		·
Nominal voltage DC	[V]	24 (±15%)			
Nominal current	[A]	3	3	5.3	
Max. current consumption (load)	[A]	3	3	5.3	
Max. current consumption (logic)	[mA]	300	'	-	
Encoder					
Rotor position encoder		Absolute encoder, single turn			
Rotor position sensor measuring principl	е	Magnetic			
Rotor position encoder resolution	[bit]	16			
Interfaces Size		32	45	60	
Parameterisation interface					
IO-Link		Yes			
User interface		Yes			
Digital inputs					
Number		2			2
Switching logic		PNP			
		NPN			
Properties		Not galvanically isolated			
		Configurable			
Specification		Based on IEC 61131-2, type 1			
Working area	[V]	24			
Digital outputs					
Number		2			
Switching logic		PNP			
		NPN			
Rotor position encoder		Absolute encoder, single turn			
Properties		Not galvanically isolated			
Management	[A]	Configurable			
Max. current	[mA]	100			


Technical data – IO-Link					
Size		32	45	60	
SIO-mode support		Yes			
Communication mode		COM3 (230.4 kBaud)			
Connection technology		Plug			
Port class		A			
Number of ports		1			
Process data width OUT	[bytes]	2			
Process data content OUT	[bit]	1 (Move in)			
	[bit]	1 (Move out)			
	[bit]	1 (Quit Error)			
Process data width IN	[bytes]	2			
Process data content IN	[bit]	1 (State Device)			
	[bit]	1 (State Move)			
	[bit]	1 (State in)			
	[bit]	1 (State out)			
Service data contents IN	[bit]	32 (Force)			
	[bit]	32 (Position)			
	[bit]	32 (Speed)			
Minimum cycle time	[ms]	1			
Data memory required	[Kilobyte]	0.5			
Protocol version		Device V 1.1			

Operating and environmental condition	ns					
Size		32	45		60	
Insulation class		В				
Ambient temperature	[°C]	0 +50				
Storage temperature	[°C]	-20 +60				
Note on ambient temperature		Above an ambient temp	perature of 30°C, the power mu	st be reduced by 2% per K		
Temperature monitoring		Switch-off for excessive	temperature			
		Integrated precise CMC	S temperature sensor with ana	logue output		
Relative humidity	[%]	0 90				
Protection class		III				
Degree of protection		IP40				
Duty cycle	[%]	100				
CE marking		To EU EMC Directive				
		To EU RoHS Directive				
KC mark		KC-EMV				
Certification		RCM compliance mark				
Vibration resistance		Transport application c	heck with severity level 1 to FN	942017-4 and EN 61800-2	and EN 61800-5-1	
Shock resistance		Shock test with severity	Shock test with severity level 1 to FN 942017-5 and EN 61800-2			
Maintenance interval		Life-time lubrication				

Weight				
Size		32	45	60
Basic weight with 0 mm stroke	[g]	889	1354	2862
Additional weight per 10 mm stroke	[g]	18	36	51
Moving mass at 0 mm stroke	[g]	83.4	220	525

Materials

Sectional view



Axis	S .			
[1]	Drive cover	Painted die-cast aluminium		
[2]	Spindle nut	Steel		
[3]	Slide	Die-cast aluminium		
[4]	Guide	Steel		
[5]	Spindle	Steel		
[6]	Cover strip	High-alloy stainless steel		
[7]	Profile	Anodised wrought aluminium alloy		
[8]	End cap	Painted die-cast aluminium		
	Note on materials	RoHS-compliant		
		Contains paint-wetting impairment substances		

Pin allocation

Power supply

Plug

M12x1, 4-pin, T-coded to EN 61076-2-111



Pin	Function	
1	Power supply (24 V DC)	
2	Reference potential, power supply (GND)	
3		
4	Functional earth (FE)	

Logic interface

Plug

M12x1, 8-pin, A-coded to EN 61076-2-101




When used with	h digital I/O	
Pin	Function	
1	Logic power supply (24 V DC)	
2	Digital output 1 (State "In")	
3	Digital output 2 (State "Out")	
4 Reference potential, logic power supply (GND)		
5	Digital input 1 (Move "In")	
6	Digital input 2 (Move "Out")	
7	Reserved, do not connect	
8 Reference potential, logic power supply (GND)		


When use	When used with I/O-Link		
Pin	Function		
1 L+ IO-Link power supply (24 V DC)			
2	Reserved, do not connect		
3	C/Q communication with the IO-Link master		
4	L – Reference potential, IO-Link power supply (0 V)		
5	Reserved, do not connect		
6	Reserved, do not connect		
7 Reserved, do not connect			
8	L – Reference potential, IO-Link power supply (0 V)		

Characteristic load values

The indicated forces and torques refer to the centre of the guide. The point of application of force is the point where the centre of the guide and the longitudinal centre of the slide intersect. These values must not be exceeded during dynamic operation. Special attention must be paid to the deceleration phase.



Distance from the slide surface to the centre of the guide



Max. permissible forces and torques on the slide (strength limits)					
Size		32	45	60	
Fy _{max} .	[N]	150	300	600	
Fz _{max} .	[N]	300	600	1800	
Mx _{max} .	[Nm]	1.3	5.5	29.1	
My _{max.}	[Nm]	1.1	4.7	31.8	
Mz _{max.}	[Nm]	1.1	4.7	31.8	

Distance from the slide surface to the centre of the guide				
Size		32	45	60
Dimension x	[mm]	31.4	42.8	54.6

Max. permissible force	Max. permissible forces and torques for the bearing calculation, for a service life of 5000 km or 5×10^6 cycles				
Size		32	45	60	
Fy _{max} .	[N]	356	880	3641	
Fz _{max} .	[N]	356	880	3641	
Mx _{max} .	[Nm]	1.3	5.5	29.1	
My _{max} .	[Nm]	1.1	4.7	31.8	
Mz _{max.}	[Nm]	1.1	4.7	31.8	



Note

For a guide system to have a service life of 5000 km, the load comparison factor must have a value of $fv \le 1$, based on the maximum permissible forces and torques for a service life of 5000 km.

This formula can be used to calculate a guide value.

The engineering software "PositioningDrives" is available

for more precise calculations → www.festo.com

If the axis is subjected to two or more of the indicated forces and torques simultaneously, the following equation must be satisfied in addition to the indicated maximum loads:

Calculating the load comparison factor:

$$f_v = \frac{\left|F_{y1}\right|}{F_{y2}} + \frac{\left|F_{z1}\right|}{F_{z2}} + \frac{\left|M_{x1}\right|}{M_{x2}} + \frac{\left|M_{y1}\right|}{M_{y2}} + \frac{\left|M_{z1}\right|}{M_{z2}} \leq 1$$

 $F_1/M_1 = dynamic value$

 $F_2/M_2 = maximum value$

Calculating the service life


The service life of the guide depends on the load. To be able to make a statement as to the service life of the guide, the graph below plots the load comparison factor fv against the service life.

These values are only theoretical. You must consult your local Festo contact for a load comparison factor fv greater than 1.

Load comparison factor fv as a function of service life l

Example:

A user wants to move an x kg load. Using the formula (\rightarrow page 12) gives a value of 1.5 for the load comparison factor fv. According to the graph, the guide has a service life of approx. 1500 km. Reducing the acceleration reduces the My and Mz values. A load comparison factor fv of 1 now gives a service life of 5000 km.



Comparison of the characteristic load values for 5000 km with dynamic forces and torques of recirculating ball bearing guides

The characteristic load values of bearing guides are standardised to ISO and JIS using dynamic and static forces and torques. These forces and torques are based on an expected service life of the guide system of 100 km according to ISO or 50 km according to JIS.

As the characteristic load values are dependent on the service life, the maximum permissible forces and torques for a 5000 km service life cannot be compared with the dynamic forces and torques of bearing guides to ISO/JIS.

To make it easier to compare the guide capacity of linear axes ELGS with bearing guides, the table below lists the theoretically permissible forces and torques for a calculated service life of 100 km. This corresponds to the dynamic forces and torques to ISO.

These 100 km values have been calculated mathematically and are only to be used for comparing with dynamic forces and torques to ISO. The drives must not be loaded with these characteristic values as this could damage the axes.

Max. permissible forces and to	lax. permissible forces and torques for a theoretical service life of 100 km (from a guide perspective only)				
Size		32	45	60	
Fy _{max} .	[N]	1310	3240	13400	
Fz _{max} .	[N]	1310	3240	13400	
Mx _{max} .	[Nm]	5	20	107	
My _{max} .	[Nm]	4	17	117	
Mz _{max} .	[Nm]	4	17	117	

Service life of the motor

The service life of the motor at nominal power is 20000 h.

Sizing example

Application data:


- Payload: 8 kg
- Mounting position: horizontal
- Stroke: 400 mm
- Max. permitted positioning time: 4 s (one direction)

Step 1: Selection of the possible size from the table → page 8

Mechanical data					
Size		32	45	60	
Max. payload	Max. payload				
Horizontal	[kg]	2	10	20	
Vertical	[kg]	2	5	13	

→ Smallest possible size: ELGS-BS-KF-45













Step 3: Reading off the min. positioning time t for stroke l






→ Min. positioning time for 400 mm at level 9: 2 s

Result


The application can be implemented using ELGS-BS-KF-45-400. A minimum positioning time (one direction) of 2 s is achieved. Longer positioning times can be selected at any time using a lower speed level.

Mass m as a function of speed level v


Size 32



Size 45



Size 60




Note:

The lines represent the maximum values. The lower speed levels can be set at any time.


----- Horizontal

Positioning time t as a function of speed level v and stroke l

Size 32



Size 45





l = 100 mm
l = 200 mm
l = 300 mm
l = 400 mm
l = 500 mm
l = 600 mm
l = 800 mm

 l = 100 mm
 l = 200 mm
 l = 300 mm
 l = 400 mm
 l = 500 mm
 l = 600 mm
 l = 800 mm


Positioning time t as a function of speed level v and stroke l


Size 60






Feed force F as a function of force level F1






Feed force F as a function of service life l





2nd moment of area





Size		32	45	60
ly	[mm ⁴]	38x10 ³	140x10 ³	441x10 ³
Iz	[mm ⁴]	45x10 ³	170x10 ³	542x10 ³


Recommended deflection limits

Adherence to the following deflection limits is recommended so as not to impair the functional performance of the axes. Greater deformation can result in increased friction, greater wear and reduced service life.

Size	Dynamic deflection (moving load)	Static deflection (stationary load)	
32 60	0.05% of the axis length, max. 0.5 mm	0.1% of the axis length	







Dimensions Download CAD data → www.festo.com Slide Size 45 Size 32 L1 L1 View A View A 모모 D2/T3 6 D1 D3 D2/T3 6 [6] Drill hole for centring pin ZBS Size D2 D3 В1 D1 Н1 H2 Ø ±0.1 ±0.1 Н8 ±0.1 For D2 ±0.03 M1.6 М3 30.5 32 4 2 22.5 45 M2 4 M4 43.5 34 6 T4¹⁾ Size L1 L2 L3 T1 T2 T3 ±0.1 ±0.1 +0.1

3.8

3

3.1

3.1

4 ... 5

6 ... 7.5

59

67.5

35

42


18

24

32

45

¹⁾ Recommended screw-in depth



T1

9

T2

T3

+0.1

1.3

T4¹⁾

8.5 ... 10

1)	Recommended	screw-in	depth
----	-------------	----------	-------

L1

88.5

L2

±0.1

58

L3

±0.1

30

Size

60

Technical data

Ordering data					
	Size	Spindle pitch	Stroke	Part no.	Туре
.B.	32	8	100	8083424	ELGS-BS-KF-32-100-8P-ST-M-H1-PLK-AA
			200	8083425	ELGS-BS-KF-32-200-8P-ST-M-H1-PLK-AA
			300	8083426	ELGS-BS-KF-32-300-8P-ST-M-H1-PLK-AA
			400	8083427	ELGS-BS-KF-32-400-8P-ST-M-H1-PLK-AA
			500	8083428	ELGS-BS-KF-32-500-8P-ST-M-H1-PLK-AA
			600	8083429	ELGS-BS-KF-32-600-8P-ST-M-H1-PLK-AA
			800	8083430	ELGS-BS-KF-32-800-8P-ST-M-H1-PLK-AA
	45	10	100	8083470	ELGS-BS-KF-45-100-10P-ST-M-H1-PLK-AA
	45	10	200	8083470	ELGS-BS-KF-45-100-10P-SI-M-H1-PLK-AA
			300		
				8083472	ELGS-BS-KF-45-300-10P-ST-M-H1-PLK-AA
			400	8083473	ELGS-BS-KF-45-400-10P-ST-M-H1-PLK-AA
			500	8083474	ELGS-BS-KF-45-500-10P-ST-M-H1-PLK-AA
			600	8083475	ELGS-BS-KF-45-600-10P-ST-M-H1-PLK-AA
			800	8083476	ELGS-BS-KF-45-800-10P-ST-M-H1-PLK-AA
	60	12	100	8083383	ELGS-BS-KF-60-100-12P-ST-M-H1-PLK-AA
			200	8083384	ELGS-BS-KF-60-200-12P-ST-M-H1-PLK-AA
			300	8083385	ELGS-BS-KF-60-300-12P-ST-M-H1-PLK-AA
			400	8083386	ELGS-BS-KF-60-400-12P-ST-M-H1-PLK-AA
			500	8083387	ELGS-BS-KF-60-500-12P-ST-M-H1-PLK-AA
			600	8083388	ELGS-BS-KF-60-600-12P-ST-M-H1-PLK-AA
			800	8083389	ELGS-BS-KF-60-800-12P-ST-M-H1-PLK-AA

Ordering data – Modular product system


Ordering table								
Size		32	45	60	Conditions	Code	Enter code	
Module no.		8083433	8083493	8083398				
Series		ELGS				ELGS	ELGS	
Drive system		Ball screw drive			-BS	-BS		
Guide		Recirculating ball bearing guid	le		-KF	-KF		
Size		32	45	60				
Stroke	[mm]	100, 200, 300, 400, 500, 600, 800	100, 200, 300, 400, 500, 600, 800	100, 200, 300, 400, 500, 600, 800				
Spindle pitch	[mm]	8P	10P	12P				
Motor type		Stepper motor ST	tepper motor ST					
Controller		Integrated		-M	-M			
Control panel		Integrated						
Bus protocol/control		NPN and IO-Link		-NLK				
		PNP and IO-Link				-PLK		
End-position sensing		With integrated end-position s	sensing			-AA	-AA	
Cable outlet direction		Standard						
		Underneath				-D		
		Rear				-B		
		Front				-F		
Electrical accessories		None						
		Adapter for operation as IO-Lir	nk device	<u> </u>		+L1		
Operating instructions		With operating instructions						
		Without operating instructions		DN				


Profile mounting EAHF-L2-...-P-S

Material:

Anodised wrought aluminium alloy RoHS-compliant

• For mounting the axis on the side of the profile





Dimensions and	Dimensions and ordering data											
For size	B1	B2	B3	D1	D2	H2						
				Ø	Ø							
				H13	H13							
32	51.4	9.7	42	4.5	8	4.9						
45	70.6	12.8	58	5.5	10	6.1						
60	85.6	12.8	73	5.5	10	6.1						


For size	H4	H5	L1	Weight	Part no.	Туре
	±0.1			[g]		
32	4.2	9	19	4	5183153	EAHF-L2-25-P-S
	г.г.	12.2	10	(5184133	EAHF-L2-45-P-S
45	5.5	12.2	19	0	3104133	LAIII-LZ-43-F-3

Profile mounting EAHF-L2-...-P

Material: Anodised wrought aluminium alloy • For mounting the axis on the side of the profile.

The profile mounting can be attached to the mounting surface using the drill hole in the centre.





Dimensions and ord	Dimensions and ordering data										
For size	B1	B2	В3	D1	D2	D3	H2				
				Ø	Ø	Ø					
				H13	H13						
32	51.4	9.7	42	4.5	8	4	4.9				
45	70.6	12.8	58	5.5	10	5	6.1				
60	85.6	12.8	73	5.5	10	5	6.1				

For size	H4	H5	L1	L2	Weight	Part no.	Туре
	±0.1				[g]		
32	4.2	9	53	40	19	4835684	EAHF-L2-25-P
45	5.5	12.2	53	40	35	4835728	EAHF-L2-45-P
60		12.2	C 2	40	35	4835728	EAHF-L2-45-P

Profile mounting EAHF-L2-...-P-D...


Material:

Anodised wrought aluminium alloy RoHS-compliant

- For axis/axis mounting without adapter plate
- Mounting option: base axis with one-size-down assembly axis (→ page 4)

Combination matrix									
[2] Assembly axis ELGC-BS/-TB; ELFC; EGSC-BS									
	Size	25	32	45	60				
[1] Base axis	32	4759753	-	-	-				
ELGC-BS/-TB; ELFC	45	_	4759748	-	-				
	60	_	_	4759739	_				





- [1] Base axis
- [2] Assembly axis

Dimensions and ordering data										
For combination	B1	B2	D1	H1						
(size)										
45/32	45	34	M4	9						
60/45	60	47	M5	12.2						

For combination (size)	H2 ±0.1	L1	L2	Weight [g]	Part no.	Туре
45/32	3.7	51.4	42	24	4759748	EAHF-L2-25-P-D2
60/45	5.5	70.6	58	56	4759739	EAHF-L2-45-P-D3

Adapter kit EHAA-D-L2


Material:

Anodised wrought aluminium alloy

RoHS-compliant

- For axis/axis mounting with adapter plate
- Mounting option: base axis with same size or one-size-down assembly axis
 (→ page 4)

Combination matrix										
[2] Assembly axis ELGC-BS/-TB; ELFC; EGSC-BS										
	Size	25	32	45	60	80				
[1] Base axis	32	8066713		-	-	-				
ELGC-BS/-TB; ELFC	45	_	8066714		-	-				
	60	_	-	8066715		_				



Dimensions and ordering data												
For combination	B1	В3	D1	H1	H2	L1	L2	L3	T1	Weight	Part no.	Туре
(size)		±0.05								[g]		
45/32	45	34	M4	19	10	51.4	42	42	5.4	136	8066714	EHAA-D-L2-45-L2-45
60/45	60	47	M5	24.2	12	70.6	58	58	5.4	205	8066715	EHAA-D-L2-60-L2-60

For combination	B1	B2	В3	D1	H1	H2	L1	L2	L3	T1	Weight	Part no.	Туре
(size)			±0.05								[g]		
45/45	45	32	34	M4	22.2	10	71	58	42	5.4	136	8066714	EHAA-D-L2-45-L2-45
60/60	60	39	47	M5	24.2	12	86	73	58	5.4	205	8066715	EHAA-D-L2-60-L2-60

Angle kit EHAA-D-L2-...-AP

Material:

Anodised wrought aluminium alloy


RoHS-compliant

• For mounting one-size-down vertical axes (assembly axes) on base axes with mounting position "slide at top"

(→ page 4)

Combination matrix					
		[2] Assembly axis ELGC-BS/-TE	B; ELFC; EGSC-BS		
	Size	25	32	45	60
[1] Base axis	32	8066717	-	-	-
[1] Base axis ELGC-BS/-TB; ELFC	32 45	8066717	- 8066718	-	-





Dimensions and order	ing data									
For combination (size)	B1	B2	В3	B4	B5	D1	H1	H2	Н3	H4
45/32	69	60	34	20.5	11.5	M4	45	17.5	10	34
60/45	87.2	75	47	21.5	11.5	M5	60	24.5	12	47


For combination (size)	H5	L1	L2	L3	T1	Weight [g]	Part no.	Туре
45/32	5.5	52	42	42	5.4	222	8066718	EHAA-D-L2-45-L2-32-AP
60/45	6.5	71	58	58	5.4	433	8066719	EHAA-D-L2-60-L2-45-AP

Switch lug EAPM-L2-SLS

For sensing using inductive proximity switches SIES-8M

Material: Galvanised steel RoHS-compliant





Dimensions and ord	Dimensions and ordering data										
For size	B1	B2	В3	D1	H1	H2	Н3	H4			
					±0.2						
32	9.2	2	1.0±0.31	M1.6	27	19	4.3	2.5			
45	9.4	2	1.2±0.31	M2	37	28	5.5	3.3			
60	9.7	2	1.3±0.31	M3	37	32	6.6	3.5			

For size	H5 ±0.2	L1 ±0.2	L2 ±0.15	L3	Weight [g]	Part no.	Туре
32	24	22	18	10	10	8067259	EAPM-L2-32-SLS
45	33	30	24	14	18	8067260	EAPM-L2-45-SLS
60	37	42	30	19	27	8067261	EAPM-L2-60-SLS


Sensor bracket EAPM-L2-SH

Material:

Anodised wrought aluminium alloy

RoHS-compliant





Dimensions and ord	ering data				
For size	B1	B2	D1	H1	H2
32, 45, 60	5.5	1.3	M4	13.4	6

For size	Н3	L1	L2	Weight [g]	Part no.	Туре
32, 45, 60	3	32	25	4	4759852	EAPM-L2-SH

Ordering data					
	For size	Description	Part no.	Туре	PE ¹⁾
Centring pin ZBS	S/centring sleeve ZBH				
	32	For slide	525273	ZBS-2	10
	45		562959	ZBS-4	
	60		189652	ZBH-5	
Clamping comp	onent EADT				
	32, 45	Tool for retensioning the cover strip	8065818	EADT-S-L5-32	1
	60		8058451	EADT-S-L5-70	

1) Packaging unit

rdering data -	Type of mounting	Switching	Electrical connection	Cable length	Part no.	Туре
	,,pe et meanting	output		[m]		1,755
O contact		<u> </u>		. ,		
	Insertable in the slot from above, flush	PNP	Cable, 3-wire	7.5	551386	SIES-8M-PS-24V-K-7,5-0E
S	with the cylinder profile		Plug M8x1, 3-pin	0.3	551387	SIES-8M-PS-24V-K-0,3-M8D
//		NPN	Cable, 3-wire	7.5	551396	SIES-8M-NS-24V-K-7,5-0E
			Plug M8x1, 3-pin	0.3	551397	SIES-8M-NS-24V-K-0,3-M8D
C contact						
1	Insertable in the slot from above, flush	PNP	Cable, 3-wire	7.5	551391	SIES-8M-PO-24V-K-7,5-0E
S	with the cylinder profile		Plug M8x1, 3-pin	0.3	551392	SIES-8M-PO-24V-K-0,3-M8D
//		NPN	Cable, 3-wire	7.5	551401	SIES-8M-NO-24V-K-7,5-0E
			Plug M8x1, 3-pin	0.3	551402	SIES-8M-NO-24V-K-0,3-M8D
	Type of mounting	Switching output	Electrical connection	Cable length [m]	Part no.	Туре
	Type of mounting	"	Electrical connection		Part no.	Туре
O contact	Type of mounting	"	Electrical connection		Part no.	Туре
O contact	Inserted in the slot from above,	"	Electrical connection Cable, 3-wire		Part no. 574335	Type SMT-8M-A-PS-24V-E-2,5-OE
O contact		output		[m]		
	Inserted in the slot from above, flush with the cylinder profile, short design	output PNP	Cable, 3-wire Plug M8x1, 3-pin	[m] 2.5 0.3	574335	SMT-8M-A-PS-24V-E-2,5-0E SMT-8M-A-PS-24V-E-0,3-M8D
	Inserted in the slot from above, flush with the cylinder profile, short design Inserted in the slot from above,	output	Cable, 3-wire	[m] 2.5	574335	SMT-8M-A-PS-24V-E-2,5-0E
	Inserted in the slot from above, flush with the cylinder profile, short design	output PNP	Cable, 3-wire Plug M8x1, 3-pin	[m] 2.5 0.3	574335 574334	SMT-8M-A-PS-24V-E-2,5-0E SMT-8M-A-PS-24V-E-0,3-M8D
C contact	Inserted in the slot from above, flush with the cylinder profile, short design Inserted in the slot from above, flush with the cylinder profile, short design	output PNP	Cable, 3-wire Plug M8x1, 3-pin	[m] 2.5 0.3	574335 574334	SMT-8M-A-PS-24V-E-2,5-OE SMT-8M-A-PS-24V-E-0,3-M8D SMT-8M-A-PO-24V-E-7,5-OE
C contact	Inserted in the slot from above, flush with the cylinder profile, short design Inserted in the slot from above, flush with the cylinder profile, short design - Connecting cables	PNP PNP	Cable, 3-wire Plug M8x1, 3-pin Cable, 3-wire	[m] 2.5 0.3 7.5	574335 574334 574340	SMT-8M-A-PS-24V-E-2,5-OE SMT-8M-A-PS-24V-E-0,3-M8D SMT-8M-A-PO-24V-E-7,5-OE Data sheets → Internet:
C contact	Inserted in the slot from above, flush with the cylinder profile, short design Inserted in the slot from above, flush with the cylinder profile, short design	PNP PNP	Cable, 3-wire Plug M8x1, 3-pin	[m] 2.5 0.3	574335 574334	SMT-8M-A-PS-24V-E-2,5-0E SMT-8M-A-PS-24V-E-0,3-M8D
C contact	Inserted in the slot from above, flush with the cylinder profile, short design Inserted in the slot from above, flush with the cylinder profile, short design - Connecting cables	PNP PNP Electrical	Cable, 3-wire Plug M8x1, 3-pin Cable, 3-wire	[m] 2.5 0.3 7.5 Cable length	574335 574334 574340	SMT-8M-A-PS-24V-E-2,5-OE SMT-8M-A-PS-24V-E-0,3-M8D SMT-8M-A-PO-24V-E-7,5-OE Data sheets → Internet:
/O contact /C contact	Inserted in the slot from above, flush with the cylinder profile, short design Inserted in the slot from above, flush with the cylinder profile, short design - Connecting cables Electrical connection, left	PNP PNP Electrical	Cable, 3-wire Plug M8x1, 3-pin Cable, 3-wire	[m] 2.5 0.3 7.5 Cable length [m]	574335 574334 574340 Part no.	SMT-8M-A-PS-24V-E-2,5-OE SMT-8M-A-PS-24V-E-0,3-M8D SMT-8M-A-PO-24V-E-7,5-OE Data sheets → Internet: Type

541338

541341

NEBU-M8W3-K-2.5-LE3

NEBU-M8W3-K-5-LE3

2.5



- Note

Proximity switches are optional and only required in order to sense any intermediate positions.

Angled socket, M8x1, 3-pin

Cable, open end, 3-wire

31


Accessories

Ordering data -	- Supply cables				Data sheets → Internet: nebl
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part no.	Туре
	Angled socket, M12x1, 4-pin	Cable, open end, 4-wire	2	8080778	NEBL-T12W4-E-2-N-LE4
)		5	8080779	NEBL-T12W4-E-5-N-LE4
			10	8080780	NEBL-T12W4-E-10-N-LE4
			15	8080781	NEBL-T12W4-E-15-N-LE4
	Straight socket, M12x1, 4-pin	Cable, open end, 4-wire	2	8080790	NEBL-T12G4-E-2-N-LE4
30			5	8080791	NEBL-T12G4-E-5-N-LE4
			10	8080792	NEBL-T12G4-E-10-N-LE4
·			15	8080793	NEBL-T12G4-E-15-N-LE4

Ordering data –	Connecting cables				Data sheets → Internet: nebc
	Electrical connection, left	Electrical connection, right	Cable length	Part no.	Туре
			[m]		
	Angled socket, M12x1, 8-pin	Cable, open end, 8-wire	2	8094476	NEBC-M12W8-E-2-N-B-LE8
			5	8094478	NEBC-M12W8-E-5-N-B-LE8
			10	8094481	NEBC-M12W8-E-10-N-B-LE8
			15	8094479	NEBC-M12W8-E-15-N-B-LE8
		Straight plug, M12x1, 8-pin	2	8080786	NEBC-M12W8-E-2-N-M12G8
			5	8080787	NEBC-M12W8-E-5-N-M12G8
Maria Maria			10	8080788	NEBC-M12W8-E-10-N-M12G8
			15	8080789	NEBC-M12W8-E-15-N-M12G8
	Straight socket, M12x1, 8-pin	Cable, open end, 8-wire	2	8094480	NEBC-M12G8-E-2-N-B-LE8
Mark 1			5	8094477	NEBC-M12G8-E-5-N-B-LE8
			10	8094482	NEBC-M12G8-E-10-N-B-LE8
			15	8094475	NEBC-M12G8-E-15-N-B-LE8
		Straight plug, M12x1, 8-pin	2	8080782	NEBC-M12G8-E-2-N-M12G8
1 STATE - 20			5	8080783	NEBC-M12G8-E-5-N-M12G8
M			10	8080784	NEBC-M12G8-E-10-N-M12G8
			15	8080785	NEBC-M12G8-E-15-N-M12G8



The cables are positioned at a 45° angle to the axis.



Ordering data − IO-Link master USB Data sheets → Internet: or							
	Description	Cable length [m]	Part no.	Туре			
	For using the unit with IO-Link An external power supply plug is additionally required (not in scope of delivery)	0.3	8091509	CDSU-1			

Ordering data – Adapter Data sheets → Internet: nefc								
	Electrical connection, left	Electrical connection, right	Cable length	Part no.	Type			
			[m]					
OLUL OLUL	Straight socket, M12x1, 8-pin	Straight plug, M12x1, 5-pin	0.3	8080777	NEFC-M12G8-0.3-M12G5-LK			

Festo - Your Partner in Automation





1 Festo Inc.

5300 Explorer Drive Mississauga, ON L4W 5G4 Canada

Festo Customer Interaction Center

Tel: 1877 463 3786 Fax: 1877 393 3786



2 Festo Pneumatic

Av. Ceylán 3, Col. Tequesquináhuac 54020 Tlalnepantla, Estado de México

Multinational Contact Center

01 800 337 8669



3 Festo Corporation

1377 Motor Parkway Suite 310 Islandia, NY 11749



Regional Service Center

7777 Columbia Road Mason, OH 45040

Festo Customer Interaction Center

1 800 993 3786 1 800 963 3786 customer.service.us@festo.com

Connect with us









