

## Soft-start and exhaust valves MS-SV, MS series, NPT

**FESTO**




**New**  
**MS...-10V24C/10V24D/10V24F**

## Soft-start and quick exhaust valves MS6N-SV-C, MS series, NPT

Peripherals overview

**FESTO**

### Soft-start and quick exhaust valve MS6N-SV-C




Note

Additional accessories:

- Module connector for combination with size MS4/MS6 or size MS9 → Internet: amv, rmv, armv
- Adapter plate for mounting on profiles → Internet: ipm-80, ipm-40-80, ipm-80-80

Supply voltage  
 10V24/10V24C

Supply voltage  
 10V24D/10V24F/10V24P





New

MS...-10V24C/10V24D/10V24F

## Soft-start and quick exhaust valves MS6N-SV-C, MS series, NPT

FESTO

Peripherals overview

Mounting attachments and accessories		Individual device		Combination		➔ Page/Internet
		Without connecting plate	With connecting plate	Without connecting plate	With connecting plate	
1	Cover cap MS6-END	–	–	■	–	ms6-end
2	Mounting plate MS6-AEND	■ <sup>1)</sup>	–	■ <sup>1)</sup>	–	ms6-aend
3	Connecting plate-SET MS6-AQ...	–	■ <sup>1)</sup>	–	■ <sup>1)</sup>	ms6-aq
4	Mounting bracket MS6-WB	■	■	–	–	ms6-wb
5	Module connector MS6-MV	–	■	■	■	ms6-mv
6	Mounting bracket MS6-WP	■	■	■	■	ms6-wp
	Mounting bracket (not shown) MS6-WPB/WPE/WPM	■	■	■	■	ms6-wp
7	Silencer U-¾-B-NPT	■	■	■	■	40
8	MS pressure gauge AG/RG	■	■	■	■	10
9	Adapter plate for EN pressure gauge ¼ A4	■	■	■	■	10
10	Pressure gauge MA	■	■	■	■	41
11	Pressure sensor with operational status indicator AD7 ... AD10	■	■	■	■	10
12	Connecting cable NEBU-M8...-LE3	■	■	■	■	41
13	Pressure sensor with LCD display AD1 ... AD4	■	■	■	■	10
14	Connecting cable NEBU-M8...-LE3/NEBU-M12...-LE4	■	■	■	■	41
15	Cover MS6-SV-C-MK	■	■	■	■	39
16	Illuminating seal MEB-LD	■	■	■	■	40
17	Plug socket with cable KMEB	■	■	■	■	40
18	Plug socket MSSD-EB	■	■	■	■	40
19	Connecting cable NEBU-M12G5	■	■	■	■	41
20	Connecting cable NEBU-M12W5	■	■	■	■	41

1) Module connector MS6-MV [5] or mounting bracket MS6-WP/WPB/WPE/WPM [6] is required for mounting.


**New**  
**MS...-10V24C/10V24D/10V24F**

## Soft-start and quick exhaust valves MS6N-SV-C, MS series, NPT


Technical data





**FESTO**

MS6N-SV-...-10V24/10V24F/10V24P



MS6N-SV-...-10V24C/10V24D



-  Flow rate  
5,700 l/min
-  Temperature range  
0 ... +60 °C
-  Operating pressure  
3 ... 10 bar
-  [www.festo.com](http://www.festo.com)

Electro-pneumatic soft-start and quick exhaust valve for gradual pressurisation and quick exhausting of system components (single channel). The main flow control valve in the cover permits a gradual build-up of output pressure p2. Once the output pressure p2 has reached the set pressure switchover point (switching pressure), the valve opens and the full operating pressure p1 is present at the output.

- Suitable for applications with high flow rates and restricted space with medium safety requirements up to controller category 1, performance level "c"
- High volumetric flow rate for pressurisation and venting
- The filling flow rate can be set via a flow control valve for gradual pressure build-up
- Adjustable pressure switchover point
- Optional pressure sensor
- Optional cover for the control sections as tamper protection

Safety characteristics	
Conforms to standard	EN ISO 13849-1
Safety function	Exhausting
	Avoidance of unexpected start-up (pressurisation)
Performance level (PL)	Exhausting: up to category 1, PL c
	Avoidance of unexpected start-up (pressurisation): up to category 1, PL c
Note on forced dynamisation	Switching frequency min. 1/month
CE marking (see declaration of conformity) <sup>1)</sup>	To EC Machinery Directive
Shock resistance	Shock test with severity level 2 according to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 2 according to FN 942017-4 and EN 60068-2-6

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

**Note on forced dynamisation: switching frequency min. 1/month**

The mechanical system is not tested in the controlled (i.e. pressurised) state. If the process-related switching

frequency (safe exhausting) is less than once a month, the machine's

operator has to carry out a forced switch off.



New

MS...-10V24C/10V24D/10V24F

## Soft-start and quick exhaust valves MS6N-SV-C, MS series, NPT

FESTO

Technical data

General technical data		
Pneumatic connection 1, 2	Female thread	NPT $\frac{1}{2}$
	Connecting plate AQ...	NPT $\frac{1}{4}$ , NPT $\frac{3}{8}$ , NPT $\frac{1}{2}$ or NPT $\frac{3}{4}$
Pneumatic connection 3		NPT $\frac{3}{4}$
Actuation type		Electric
Design		Piston spool valve
Type of mounting		Via accessories
		In-line installation
Mounting position		Any
Pressure indicator		Via pressure sensor for displaying output pressure via LCD display and electrical output
		Via pressure sensor for displaying output pressure via operational status indicator and electrical output
		Via pressure gauge for displaying output pressure
		Via pressure gauge with red/green scale for displaying output pressure
		G $\frac{1}{4}$ prepared
Valve function		3/2-way valve, closed, single solenoid
		Soft-start function, adjustable
Non-overlapping		Yes
Exhaust function		No flow control
Manual override	10V24/10V24F	At the pilot solenoid valve: non-detenting
		At the soft-start and quick exhaust valve: detenting, self-resetting
	10V24P	At the pilot solenoid valve: non-detenting/detenting
		At the soft-start and quick exhaust valve: detenting, self-resetting
	10V24C/10V24D	None
Reset method		Mechanical spring
Type of control		Piloted
Pilot air supply		Internal
Sealing principle		Soft

Flow rate characteristics		
Pneumatic connection		Female thread NPT $\frac{1}{2}$
Standard nominal flow rate $q_{nN}^{1)}$ [l/min]		
In main flow direction 1 $\rightarrow$ 2		5,700
Standard flow rate $q_N$ [l/min], $p_2 = 6$ bar		
In venting direction 2 $\rightarrow$ 3		7,600 <sup>2)</sup>
C value [l/s*min]		
In main flow direction 1 $\rightarrow$ 2		23.2
b value		
In main flow direction 1 $\rightarrow$ 2		0.4

1) Measured at  $p_1 = 6$  bar and  $p_2 = 5$  bar,  $\Delta p = 1$  bar

2) Measured with respect to atmosphere with silencer S

Electrical data		
Coil characteristics	10V24/10V24P	24 V DC: 1.8 W; permissible voltage fluctuations $-10\%/+10\%$
	10V24C/10V24D/ 10V24F	24 V DC: 1.8 W; permissible voltage fluctuations $-15\%/+10\%$
Electrical connection	10V24/10V24C	Plug, 2-pin, to EN 175301-803, type C
	10V24D/10V24F/ 10V24P	M12x1 to ISO 20401 suitable to EN 61076-2-101
Protection class		IP65 with plug socket
Duty cycle	[%]	100
Switching time off	[ms]	65
Switching time on	[ms]	370

## Soft-start and quick exhaust valves MS6N-SV-C, MS series, NPT

Technical data

Operating and environmental conditions	
Operating pressure [bar]	3 ... 10
Operating medium	Compressed air according to ISO 8573-1:2010 [7:4:4]
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Ambient temperature [°C]	0 ... +60 (0 ... +50) <sup>1)</sup>
Temperature of medium [°C]	0 ... +60 (0 ... +50) <sup>1)</sup>
Storage temperature [°C]	-10 ... +60 (0 ... +50) <sup>1)</sup>
Corrosion resistance class CRC <sup>2)</sup>	2
CE marking (see declaration of conformity) <sup>3)</sup>	To EU Machinery Directive
Food-safe <sup>3)</sup>	See supplementary material information (except solenoid valve)

1) With pressure sensor AD...

2) Corrosion resistance class CRC 2 to Festo standard FN 940070


Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

3) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

Weight [g]	
Soft-start and quick exhaust valve	886
Soft-start and quick exhaust valve with silencer S	1,006

Materials	
Housing	Die-cast aluminium
Piston rod	High-alloy stainless steel
Seals	NBR
Note on materials	RoHS-compliant

### Adjusting elements



1 Screw for adjusting the pressure switchover point

2 Flow control screw for adjusting the filling time

3 Manual override at the soft-start and quick exhaust valve:

- Detenting, self-resetting as soon as the solenoid coil or manual override at the pilot solenoid valve is actuated (with 10V24/10V24F/ 10V24P)
- None (with 10V24C/10V24D)

4 Manual override at the pilot solenoid valve:

- Non-detenting, actuation from above (with 10V24/10V24F)
- Non-detenting/detenting, actuation from above (with 10V24P)
- None (with 10V24C/10V24D)

## Soft-start and quick exhaust valves MS6N-SV-C, MS series, NPT


**FESTO**

Technical data

### Dimensions – Basic design

Download CAD data → [www.festo.com](http://www.festo.com)

With female thread NPT $\frac{1}{2}$ , with cover plate



Type	B1	B4	B5	D1	D2	D5	L1	L2	L4
MS6N-SV-C	62	31	76	NPT $\frac{1}{2}$	M12x1	NPT $\frac{3}{4}$	144	71	135

Type	L8		L9	
	10V24/10V24C	10V24D/10V24F/10V24P	10V24/10V24C	10V24D/10V24F/10V24P
MS6N-SV-C	33	37	24	26



New

MS...-10V24C/10V24D/10V24F

## Soft-start and quick exhaust valves MS6N-SV-C, MS series, NPT

FESTO


Technical data

### Dimensions – Pressure gauge/pressure gauge alternatives

Download CAD data → [www.festo.com](http://www.festo.com)

Integrated MS pressure gauge with standard scale AG or red/green scale RG

Adapter plate A4 for EN pressure gauge  $\frac{1}{4}$ , without pressure gauge



Type	B4	B5	D4
MS6N-SV-...-AG	31	77	–
MS6N-SV-...-RG	31	78.5	–
MS6N-SV-...-A4	31	78.5	G $\frac{1}{4}$



## Soft-start and quick exhaust valves MS6N-SV-C, MS series, NPT

**FESTO**


Technical data

### Dimensions – Pressure gauge/pressure gauge alternatives

Download CAD data → [www.festo.com](http://www.festo.com)

Pressure sensor with LCD display AD1 ... AD4

Technical data → Internet: [sde1](#)



Variant AD1:  
SDE1-D10-G2-MS-L-P1-M8 with  
3-pin plug M8x1, 1 switching out-  
put PNP


Variant AD2:  
SDE1-D10-G2-MS-L-N1-M8 with  
3-pin plug M8x1, 1 switching out-  
put NPN

Variant AD3:  
SDE1-D10-G2-MS-L-PI-M12 with  
4-pin plug M12x1, 1 switching out-  
put PNP and 4 ... 20 mA analogue

Variant AD4:  
SDE1-D10-G2-MS-L-NI-M12 with  
4-pin plug M12x1, 1 switching out-  
put NPN and 4 ... 20 mA analogue

### Pressure sensor with operational status indicator AD7 ... AD10

Technical data → Internet: [sde5](#)



Variant AD7:  
SDE5-D10-O-...-P-M8 with 3-pin  
plug M8x1, threshold value compar-  
ator, 1 switching output PNP, N/O  
contact

Variant AD8:  
SDE5-D10-C-...-P-M8 with 3-pin  
plug M8x1, threshold value compar-  
ator, 1 switching output PNP, N/C  
contact

Variant AD9:  
SDE5-D10-O3-...-P-M8 with 3-pin  
plug M8x1, window comparator, 1  
switching output PNP, N/O contact

Variant AD10:  
SDE5-D10-C3-...-P-M8 with 3-pin  
plug M8x1, window comparator, 1  
switching output PNP, N/C contact

Type	B4	B5	B6	D6	L5	L6
MS6N-SV-...-AD1/AD2	31	102	32.3	M8x1	35.1	46.7
MS6N-SV-...-AD3/AD4				M12x1		55.8
MS6N-SV-...-AD7/AD8/AD9/AD10	31	79	–	M8x1	–	–

## Soft-start and quick exhaust valves MS6N-SV-C, MS series, NPT

Ordering data – Modular products

Mandatory data							
Module No.	Series	Size	Thread	Function	Pneumatic connection	Performance level	Supply voltage
548714	MS	6	N	SV	1/2, AQ...	C	10V24, 10V24C, 10V24D, 10V24F, 10V24P
<b>Ordering example</b>							
548714	MS	6	N	- SV	- AQP	- C	- 10V24

Ordering table					
Grid dimension	[mm]	62	Condi- tions	Code	Enter code
M	Module No.	548714			
	Series	Standard		MS	MS
	Size	6		6	6
	Thread	NPT thread		N	N
	Function	Soft-start and quick exhaust valve		-SV	-SV
	Pneumatic connection	Female thread NPT1/2		-1/2	
		Connecting plate NPT1/4		-AQN	
		Connecting plate NPT3/8		-AQP	
		Connecting plate NPT1/2		-AQR	
		Connecting plate NPT3/4		-AQS	
	Performance level	Category 1, 1-channel, to EN ISO 13849-1		-C	-C
	Supply voltage	24 V DC (pin allocation to EN 175301), 3 ... 10 bar, manual override		-10V24	
		– at the soft-start and quick exhaust valve: detenting, self-resetting			
		– at the pilot solenoid valve: non-detenting			
		24 V DC (pin allocation to EN 175301), 3 ... 10 bar, none manual override		-10V24C	
		24 V DC, M12x1 to ISO 20401 suitable to EN 61076-2-101, 3 ... 10 bar, none manual override		-10V24D	
		24 V DC, M12x1 to ISO 20401 suitable to EN 61076-2-101, 3 ... 10 bar, manual override		-10V24F	
		– at the soft-start and quick exhaust valve: detenting, self-resetting			
		– at the pilot solenoid valve: non-detenting			
		24 V DC, M12x1 to ISO 20401 suitable to EN 61076-2-101, 3 ... 10 bar, manual override		-10V24P	
		– at the soft-start and quick exhaust valve: detenting, self-resetting			
		– at the pilot solenoid valve: non-detenting/detenting			

### Transfer order code

548714	MS	6	N	-	SV	-		-	C	-	
--------	----	---	---	---	----	---	--	---	---	---	--

## Soft-start and quick exhaust valves MS6N-SV-C, MS series, NPT

**FESTO**

Ordering data – Modular products

→ 0 Options					
Silencer	Pressure gauge/ pressure gauge alternatives	Alternative pressure gauge scale	Type of mounting	Tamper protection	Flow direction
S	AG, A4, RG, AD1 ... AD4, AD7 ... AD10	BAR, MPA	WP, WPM, WPB, WB	MK	Z
- S	- AG	-	- WP	-	-

Ordering table					
Grid dimension	[mm]	62	Condi- tions	Code	Enter code
0 Silencer	Silencer			-S	
Pressure gauge/pressure gauge alternatives	MS pressure gauge		1	-AG	
	Adapter plate for EN pressure gauge 1/4, without pressure gauge			-A4	
	Integrated pressure gauge, red/green scale		1	-RG	
	Pressure sensor with LCD display, plug M8, 1 switching output PNP, 3-pin		2	-AD1	
	Pressure sensor with LCD display, plug M8, 1 switching output NPN, 3-pin		2	-AD2	
	Pressure sensor with LCD display, plug M12, 1 switching output PNP, 4-pin, analogue output 4 ... 20 mA		2	-AD3	
	Pressure sensor with LCD display, plug M12, 1 switching output NPN, 4-pin, analogue output 4 ... 20 mA		2	-AD4	
	Pressure sensor with operational status indicator, plug M8, threshold value comparator, PNP, N/O contact		2	-AD7	
	Pressure sensor with operational status indicator, plug M8, threshold value comparator, PNP, N/C contact		2	-AD8	
	Pressure sensor with operational status indicator, plug M8, window comparator, PNP, N/O contact		2	-AD9	
Alternative pressure gauge scale	bar		3	-BAR	
	MPa		3	-MPA	
Type of mounting	Mounting bracket standard design			-WP	
	Mounting bracket for attaching the service units		4	-WPM	
	Mounting bracket for large wall gap			-WPB	
	Mounting bracket centrally at rear (wall mounting top and bottom), connecting plates not required			-WB	
Tamper protection	Complete (manual override at soft-start/quick exhaust valve locked, adjusting screw locked, manual override at pilot solenoid valve locked (only with supply voltage 10V24, 10V24P))			-MK	
Flow direction	Flow direction from right to left			-Z	

- 1 **AG, RG** Pressure gauge scale in psi.  
 With pressure gauge RG: PSI scale serves only as an auxiliary scale (inner scale),  
 outer scale in bar
- 2 **AD1 ... AD4, AD7 ... AD10**  
 Measuring range max. 10 bar
- 3 **BAR, MPA** Only in combination with pressure gauge AG or RG
- 4 **WPM** Only with connecting plate AQN, AQP, AQR or AQS

### Transfer order code


-  -  -  -  -  -

# Soft-start and quick exhaust valves MS6N-SV-D, MS series, NPT

FESTO


Peripherals overview

## Soft-start and quick exhaust valve MS6N-SV-D



Supply voltage  
10V24

Supply voltage  
10V24P



# Soft-start and quick exhaust valves MS6N-SV-D, MS series, NPT

Peripherals overview

Mounting components and accessories						
		Individual device		Combination		➔ Page/Internet
		Without connecting plate	With connecting plate	Without connecting plate	With connecting plate	
1	Cover cap MS6-END	–	–	■	–	ms6-end
2	Mounting plate MS6-AEND	■ <sup>1)</sup>	–	■ <sup>1)</sup>	–	ms6-aend
3	Connecting plate kit MS6-AQ...	–	■ <sup>1)</sup>	–	■ <sup>1)</sup>	ms6-aq
4	Mounting bracket MS6-WB	■	■	–	–	ms6-wb
5	Module connector MS6-MV	–	■	■	■	ms6-mv
6	Mounting bracket MS6-WP	■	■	■	■	ms6-wp
	Mounting bracket (not shown) MS6-WPB/WPE/WPM	■	■	■	■	ms6-wp
7	MS pressure gauge AG/RG	■	■	■	■	22
8	Adapter for EN pressure gauge ¼ A4	■	■	■	■	22
9	Pressure gauge MA	■	■	■	■	41
10	Pressure sensor with LCD display AD1 ... AD4	■	■	■	■	22
11	Connecting cable NEBU-M8...-LE3/NEBU-M12...-LE4	■	■	■	■	41
12	Proximity sensor 2M8/S3, SMT-8M-A-...-M8D	■	■	■	■	22, 40
13	Proximity sensor 2M12/S3, SMT-8M-A-...-M12	■	■	■	■	22, 40
14	Proximity sensor 2OE/S3, SMT-8M-A-...-OE	■	■	■	■	22, 40
15	Pneumatic Silencer SO, UOS-1	■	■	■	■	22, 38
16	Pneumatic Silencer UOS-1-LF	■	■	■	■	38
17	Illuminating seal MEB-LD	■	■	■	■	40
18	Plug socket with cable KMEB	■	■	■	■	40
19	Plug socket MSSD-EB	■	■	■	■	40
20	Connecting cable NEBU-M12G5	■	■	■	■	41
21	Connecting cable NEBU-M12W5	■	■	■	■	41


1) Module connector MS6-MV [5] or mounting bracket MS6-WP/WPB/WPE/WPM [6] is required for mounting.

# Soft-start and quick exhaust valves MS6N-SV-D, MS series, NPT

FESTO

Technical data

## Function



- - Flow rate  
4300 l/min
- - Temperature range  
-10 ... +50 °C
- - Operating pressure  
3.5 ... 10 bar
- - [www.festo.com](http://www.festo.com)



The electropneumatic soft-start and quick exhaust valve is used to reduce pressure quickly and safely and to build up pressure gradually in industrial pneumatic piping systems and terminal equipment.

The MS6N-SV-D has two safety functions:

- pressure release
- protection from unexpected start-up (non-switching)

The MS6N-SV-D has a 2-channel structure, i.e. it has two internal 2-way

valves which can be controlled separately by pilot valves (V1 and V2) situated on the cover. These valves are actuated when both coils are energised simultaneously; this changes the MS6N-SV-D from the normal position to the switching position. The outlet pressure p2 rises slowly in accordance with the throttle setting. The main seat opens when the switch-through pressure is reached. The normal position is achieved by switching off both coils.

Two proximity sensors (S1 and S2) secured on the housing monitor the directional control valves. A further proximity sensor (S3) can optionally be added to monitor the soft-start valve.

The MS6N-SV-D can achieve various categories and safety levels to EN ISO 13849-1 depending on how the directional control valves are monitored.

Where there is appropriate integration into the control chain as well as

appropriate linking of the signals for initial position sensing with the signals for activation (plausibility checking):

- Performance Level d/category 3 to EN ISO 13849-1 and EN ISO 13849-2 can be achieved when using sensors S1 and S2 and
- Performance Level e/category 4 to EN ISO 13849-1 and EN ISO 13849-2 can be achieved when using sensors S1, S2 and S3.

## - - Note

To avoid back pressures, it is recommended that the device be operated together with the silencer UOS-1. The silencer can be ordered via the modular product system (SO → 30) or as an accessory (UOS-1 → 58).

## - - Note

Only devices that do not impair pressure release may be positioned downstream of the MS6N-SV-...-D. The MS6N-SV-...-D is not permitted for use as a press safety valve.

- Conforms to standard IEC 61508
- Switching time delay adjustable via a flow control valve for gradual pressure build-up; main seat opens at approx. 50% of operating pressure
- Optional pressure sensor

## Soft-start and quick exhaust valves MS6N-SV-D, MS series, NPT

FESTO

Technical data

Safety characteristics		
Conforms to standard		EN ISO 13849-1 and EN ISO 13849-2
Safety function		Exhausting
		Avoidance of unexpected start-up (pressurisation)
Performance Level (PL)	With sensing by S1 and S2	Exhausting: category 3, PL d or category 3, PL e <sup>1)</sup>
		Avoidance of unexpected start-up (pressurisation): category 3, PL d or category 3, PL e <sup>1)</sup>
	With sensing by S1, S2 and S3	Exhausting: category 4, PL e
		Avoidance of unexpected start-up (pressurisation): category 4, PL e
Safety integrity level (SIL)		Exhausting: SIL 3
		Avoidance of unexpected start-up (pressurisation): SIL 3
Note on forced dynamisation		Switching frequency min. 1/month
CE marking (see declaration of conformity) <sup>2)</sup>		To EC Machinery Directive
Shock resistance		Shock test with severity level 2 according to FN 942017-5 and EN 60068-2-27
Vibration resistance		Transport application test with severity level 2 according to FN 942017-4 and EN 60068-2-6

1) Dependent on the average number of annual actuations ( $n_{op}$ ).

2) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.



### Note on forced dynamisation: switching frequency min. 1/month

The mechanical system is not tested in the controlled (i.e. pressurised) state. If the process-related switching

frequency (safe exhausting) is less than once a month, the machine's

operator has to carry out a forced switch off.

# Soft-start and quick exhaust valves MS6N-SV-D, MS series, NPT

FESTO


Technical data

Switching logic						
	Voltage at the pilot valve		Switching position Proximity sensor			Status
	V1	V2	S1	S2	S3	
In the normal position (completely exhausted MS6N-SV-D), the pilot valves V1 and V2 are not actuated. If both pilot valves are actuated, the MS6N-SV-D switches first into switching position 1 and then, when the switch-through pressure is reached, automatically into switching position 2.	0 V	0 V	1	1	1	<b>Normal position</b> Pneumatic port 1 closed, passage from pneumatic port 2 to 3 open
	24 V	0 V	0	1	1	<b>Normal position</b> Pneumatic port 1 closed, passage from pneumatic port 2 to 3 open
	0 V	24 V	1	0	1	<b>Normal position</b> Reduced flow through flow control valve from pneumatic port 1 to 2, passage from pneumatic port 2 to 3 open
	24 V	24 V	0	0	1	<b>Switching element position 1</b> Reduced flow through flow control valve from pneumatic port 1 to 2, passage from pneumatic port 2 to 3 closed
	24 V	24 V	0	0	0	<b>Switching position 2</b> Full flow from pneumatic port 1 to 2, passage from pneumatic port 2 to 3 closed

Proximity sensor response times <sup>1)</sup>		
Proximity sensor	Switching on	Switching off
S1	Edge change max. 4 s after voltage signal at V1.	Edge change max. 4 s after voltage drop at V1.
S2	Edge change max. 4 s after voltage signal at V2.	Edge change max. 4 s after voltage drop at V2.
S3	Edge change after voltage signal at V1 and V2. Dependent on operating pressure p1, throttle position and system volume p2	Edge change max. 5 s after voltage drop at V1 and V2. Dependent on system volume at p2.

1) When the proximity sensors undergo an edge change, bounce can occur. This bounce can be ignored by taking the response times into account.  
The maximum specified response times must be considered in the diagnostics. The response times are normally shorter.

## Example circuit



- A1, A2: Supply voltage
- S1: Proximity sensor S1
- S2: Proximity sensor S2
- S3: Proximity sensor S3
- NH: Emergency stop (input circuit)
- Safety device: Safety switching device or safety PLC
- V1: Coil connection, pilot valve V1
- V2: Coil connection, pilot valve V2
- Y1: Diagnostic input 1
- Y2: Diagnostic input 2
- Y3: Diagnostic input 3
- S: Monitored start (start circuit)



# Soft-start and quick exhaust valves MS6N-SV-D, MS series, NPT

FESTO

Technical data

General technical data	
Pneumatic port 1, 2	
Female thread	NPT $\frac{1}{2}$
Connecting plate AQ...	NPT $\frac{1}{4}$ , NPT $\frac{3}{8}$ , NPT $\frac{1}{2}$ or NPT $\frac{3}{4}$
Pneumatic port 3	NPT1
Actuation type	Electric
Design	Piston seat
Type of mounting	Via accessories
	In-line installation
Mounting position	Any
Pressure indicator	Via pressure sensor for displaying output pressure via LCD display and electrical output
	Via pressure gauge for displaying output pressure
	Via pressure gauge with red/green scale for displaying output pressure
	G $\frac{1}{4}$ prepared
Position sensing principle	Magnetic piston principle
Valve function	3/2-way valve, closed, single solenoid
	Soft-start function, adjustable
Non-overlapping	No
Exhaust function	No flow control
Manual override	None
Reset method	Mechanical spring
Type of control	Piloted
Pilot air supply	Internal
Sealing principle	Soft

Flow rate characteristics	
Pneumatic connection	Female thread NPT $\frac{1}{2}$
Standard nominal flow rate $q_{N1}$ [l/min]	
In main flow direction 1 $\rightarrow$ 2	4300
Standard flow rate $q_N$ [l/min], $p_2 = 6$ bar	
In venting direction 2 $\rightarrow$ 3	9000 <sup>2)</sup>
C value [l/s*min]	
In main flow direction 1 $\rightarrow$ 2	19.3
b value	
In main flow direction 1 $\rightarrow$ 2	0.21

1) Measured at  $p_1 = 6$  bar and  $p_2 = 5$  bar,  $\Delta p = 1$  bar

2) Measured with respect to atmosphere with silencer UOS-1

# Soft-start and quick exhaust valves MS6N-SV-D, MS series, NPT

FESTO

Technical data

Electrical data		
Pilot valve		
Coil characteristics		24 V DC: 1.8 W; permissible voltage fluctuations -15%/+10%
Electrical connection	10V24	2 x plug connectors, 2-pin, to EN 175301-803, type C
	10V24P	2 x M12x1 to ISO 20401 suitable to EN 61076-2-101
Degree of protection		IP65 with plug socket
Duty cycle	[%]	100
Max. switching frequency	[Hz]	1
Switching time off	[ms]	40
Switching time on	[ms]	130
Proximity sensor		
Nominal operating voltage	[V DC]	24
Electrical connection, proximity sensor	2M8	2 x cables with plug connector M8x1, 3-pin, rotatable thread, cable length 0.3 m
	2M12	2 x cables with plug connector M12x1, 3-pin, rotatable thread, cable length 0.3 m
	2OE	2 x cable with open end, 3-wire, cable length 5 m
	2M8 + S3	3 x cables with plug connector M8x1, 3-pin, rotatable thread, cable length 0.3 m
	2M12 + S3	3 x cables with plug connector M12x1, 3-pin, rotatable thread, cable length 0.3 m
	2OE + S3	3 x cable with open end, 3-wire, cable length 5 m
Switching element function		N/O contact
Measuring principle		Magneto-resistive
Signal status display		LED and switching outputs
Switching output		PNP
Operating and environmental conditions		
Operating pressure	[bar]	3.5 ... 10
Operating medium		Compressed air according to ISO 8573-1:2010 [7:4:4]
Note on operating/pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)
Ambient temperature	[°C]	-10 ... +50 (0 ... +50) <sup>1)</sup>
Temperature of medium	[°C]	-10 ... +50 (0 ... +50) <sup>1)</sup>
Storage temperature	[°C]	-10 ... +50 (0 ... +50) <sup>1)</sup>
Corrosion resistance class CRC <sup>2)</sup>		2
Noise level	[dB(A)]	75 (with silencer UOS-1)
CE marking (see declaration of conformity) <sup>3)</sup>		To EU Machinery Directive
UL certification <sup>3)</sup>		c UL us - Recognized (OL)
Certification		RCM Mark
KC marking		KC EMC

1) With pressure sensor AD...

2) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

3) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

## Soft-start and quick exhaust valves MS6N-SV-D, MS series, NPT

FESTO


Technical data


Weight [g]	
Soft-start/quick exhaust valve	1900
Soft-start/quick exhaust valve with silencer UOS-1	2110

Materials	
Housing	Die-cast aluminium
Piston rod	High-alloy stainless steel
Seals	NBR
Note on materials	RoHS-compliant

### Switch-through pressure

Pressure  $p$  as a function of time  $t$



 Note

The +20%/–10% switch-through pressure tolerance refers to the operating pressure  $p_1$ .  
Example: A switch-through pressure from 1.6 bar to 2.8 bar is permissible at an operating pressure of 4 bar.

# Soft-start and quick exhaust valves MS6N-SV-D, MS series, NPT

FESTO


Technical data

## Dimensions – Basic design

Download CAD data → [www.festo.com](http://www.festo.com)

With supply voltage 10V24, with female thread NPT $\frac{1}{2}$ ,  
with cover plate

With supply voltage 10V24P, with female thread NPT $\frac{1}{2}$ ,  
with cover plate



- 1 Regulating screw for flow control valve
- 2 Silencer UOS-1
- 3 Extended sensing, variant S3: additional third proximity sensor SMT, port depends on connection technology chosen 4

- 4 Connection technology,
  - variant 2M8: 2 proximity sensors SMT with cable (plug connector M8x1, 3-pin, rotatable thread, cable length 0.3 m)
  - variant 2M12: 2 proximity sensors SMT with cable (plug connector M12x1, 3-pin, rotatable thread, cable length 0.3 m)
  - variant 20E: 2 proximity sensors SMT with cable (open end, 3-wire, cable length 5 m)

- 5 Supply voltage,
  - variant 10V24: Electrical connection to EN 175301-803, 2 x plug connectors, 2-pin, type C
  - variant 10V24P: Electrical connection 2 x M12x1 to ISO 20401 suitable to EN 61076-2-101, version 4 pin for connecting cable NEBU-M12

Type	B1	B2	B3	B4	B5	D1	D5	D6 Ø	L1	L2	L4	L7	L9
MS6N-SV- $\frac{1}{2}$ -D-10V24	62	45	90	31	76	NPT $\frac{1}{2}$	NPT1	55	257	110	147	147	9
MS6N-SV- $\frac{1}{2}$ -D-10V24P									262	115			11

# Soft-start and quick exhaust valves MS6N-SV-D, MS series, NPT

FESTO


Technical data

## Dimensions – Pressure gauge/pressure gauge alternatives

Download CAD data → [www.festo.com](http://www.festo.com)

Integrated MS pressure gauge with standard scale AG or red/green scale RG

Adapter A4 for EN pressure gauge 1/4, without pressure gauge




Type	B2	B3	B4	B5	D4
MS6N-SV-...-D-...-AG	44	90	31	77	–
MS6N-SV-...-D-...-RG	44	91.5	31	78.5	–
MS6N-SV-...-D-...-A4	44	91.5	31	78.5	G1/4

## Dimensions – Pressure gauge/pressure gauge alternatives

Download CAD data → [www.festo.com](http://www.festo.com)

Pressure sensor with LCD display AD1 ... AD4

Technical data → Internet: [sde1](http://sde1.festo.com)



Type	B2	B3	B4	B5	D6	L5	L6
MS6N-SV-...-D-...-AD1/AD2	44	116	31	103	M8x1	31.2	46.8
MS6N-SV-...-D-...-AD3/AD4					M12x1		55.8

# Soft-start and quick exhaust valves MS6N-SV-D, MS series, NPT

FESTO

Ordering data – Modular products

Mandatory data →								
Module no.	Series	Size	Thread	Function	Pneumatic connection	Performance Level	Supply voltage	Connection technology
548714	MS	6	N	SV	1/2, AQ...	D	10V24, 10V24P	2M8, 2M12, 20E
Ordering example								
548714	MS	6	N	SV	AQR	D	10V24	20E

Ordering table					
Grid dimension	[mm]	62	Condi- tions	Code	Entry code
M	Module no.	548714			
	Series	Standard		MS	MS
	Size	6		6	6
	Thread	NPT thread		N	N
	Function	Soft-start and quick exhaust valve		-SV	-SV
	Pneumatic connection	Female thread NPT1/2		-1/2	
		Connecting plate NPT1/4		-AQN	
		Connecting plate NPT3/8		-AQP	
		Connecting plate NPT1/2		-AQR	
		Connecting plate NPT3/4		-AQS	
	Performance Level	Category 3, 2-channel, to EN ISO 13849-1		-D	-D
	Supply voltage	24 V DC (pin allocation to EN 175301)		-10V24	
		24 V DC, M12x1 to ISO 20401 suitable to EN 61076-2-101		-10V24P	
	Connection technology	2 proximity sensors SMT with cable plug connector M8x1, 3-pin, rotatable thread, cable length 0.3 m)		-2M8	
		2 proximity sensors SMT with cable (plug connector M12x1, 3-pin, rotatable thread, cable length 0.3 m)		-2M12	
		2 proximity sensors SMT with cable (open end, 3-wire, cable length 5 m)		-20E	

Transfer order code

548714	MS	6	N	SV		D		
--------	----	---	---	----	--	---	--	--

# Soft-start and quick exhaust valves MS6N-SV-D, MS series, NPT

FESTO

Ordering data – Modular products

Options						
Extended sensing	Silencer	Pressure gauge/ pressure gauge alternatives	Alternative pressure gauge scale	Type of mounting	UL certification	Flow direction
S3	S0	AG, A4, RG, AD1 ... AD4	BAR, MPA	WP, WPM, WPB, WB	UL1	Z
- S3	- S0	- AG	-	- WPB	-	-

Ordering table						
Grid dimension	[mm]	62	Condi- tions	Code	Entry code	
Extended sensing	Additional proximity sensor SMT; required to achieve Performance Level e; port depends on connection technology chosen			-S3		
Silencer	Silencer open			-S0		
Pressure gauge/pressure gauge alternatives	MS pressure gauge		1	-AG		
	Adapter for EN pressure gauge 1/4, without pressure gauge			-A4		
	Integrated pressure gauge, red/green scale		1	-RG		
	Pressure sensor with LCD display, plug connector M8, 1 switching output PNP, 3-pin			-AD1		
	Pressure sensor with LCD display, plug connector M8, 1 switching output NPN, 3-pin			-AD2		
	Pressure sensor with LCD display, plug connector M12, 1 switching output PNP, 4-pin, analogue output 4 ... 20 mA			-AD3		
	Pressure sensor with LCD display, plug connector M12, 1 switching output NPN, 4-pin, analogue output 4 ... 20 mA			-AD4		
Alternative pressure gauge scale	bar		2	-BAR		
	MPa		2	-MPA		
Type of mounting	Mounting bracket standard design			-WP		
	Mounting bracket for attaching the service units		3	-WPM		
	Mounting bracket for large wall gap			-WPB		
	Mounting bracket centrally at rear (wall mounting top and bottom), connecting plates not required			-WB		
UL certification	cULus, ordinary location for Canada and USA			-UL1		
Flow direction	Flow direction from right to left			-Z		

- 1 **AG, RG** Pressure gauge scale in psi.  
With pressure gauge RG: PSI scale serves only as an auxiliary scale (inner scale), outer scale in bar
- 2 **BAR, MPA** Only in combination with pressure gauge AG or RG.
- 3 **WPM** Only with connecting plates AQN, AQP, AQR or AQS

Transfer order code


- [ ] - [ ] - [ ] - [ ] - [ ] - [ ] - [ ]

# Soft-start and quick exhaust valves MS6N-SV-E, MS series, NPT

FESTO

Peripherals overview

## Soft-start and quick exhaust valve MS6N-SV-E



Note

Additional accessories:

- Module connector for combination with size MS4/MS6 or size MS9 → Internet: amv, rmv, armv
- Adapter plate for mounting on profiles → Internet: ipm-80, ipm-40-80, ipm-80-80



# Soft-start and quick exhaust valves MS6N-SV-E, MS series, NPT

Peripherals overview

Mounting attachments and accessories						
		Individual device		Combination		➔ Page/Internet
		Without connect- ing plate	With connecting plate	Without connect- ing plate	With connecting plate	
1	Cover cap MS6-END	–	–	■	–	ms6-end
2	Mounting plate MS6-AEND	■ <sup>1)</sup>	–	■ <sup>1)</sup>	–	ms6-aend
3	Connecting plate-SET MS6-AQ...	–	■ <sup>1)</sup>	–	■ <sup>1)</sup>	ms6-aq
4	Module connector MS6-MV	–	–	■	■	ms6-mv
5	Mounting bracket MS6-WPB	■	■	■	■	ms6-wpb
6	Mounting bracket MS6-WPE	■	■	■	■	ms6-wpe
7	MS pressure gauge AG/RG	■	■	■	■	34
8	Adapter plate for EN pressure gauge 1/4 A4	■	■	■	■	34
9	Pressure gauge MA	■	■	■	■	41
10	Pressure sensor with LCD display AD1 ... AD4	■	■	■	■	34
11	Connecting cable NEBU-M8...-LE3/NEBU-M12...-LE4	■	■	■	■	41
12	Multi-pin plug socket NECA	■	■	■	■	36
13	AS-i configuration plug CACC	■	■	■	■	39
14	Addressing cable KASI-ADR	■	■	■	■	kasi-asi
15	Addressing device ASI-PRG-ADR	■	■	■	■	asi-prg-adr
16	Adapter AD	■	■	■	■	40
17	Silencer UOS-1	■	■	■	■	38
18	Silencer UOS-1-LF	■	■	■	■	38


1) Module connector MS6-MV or mounting bracket MS6-WPB/WPE is required for mounting.

# Soft-start and quick exhaust valves MS6N-SV-E, MS series, NPT

FESTO

Technical data

## Function



- Flow rate  
4,300 l/min
- Temperature range  
-10 ... +50 °C
- Operating pressure  
3.5 ... 10 bar
- [www.festo.com](http://www.festo.com)



The electro-pneumatic soft-start and quick exhaust valve is used to reduce pressure quickly and reliably and to build up pressure gradually in industrial pneumatic systems and terminals. The device is a self-testing, redundant mechatronic system conforming to the

requirements of EN ISO 13849-1. The safety-related pneumatic protection objective of safe venting is also guaranteed in the event of faults inside the valve (e.g. due to wear, contamination, electronic faults). Thanks to the 2-channel design and its monitoring, the device fulfils controller category 3

and 4 requirements. This enables a performance level of max. "e" to be attained. The device receives the secure enable signals (EN1/EN2) via the electrical connection (multi-pin plug socket NECA Sub-D, 9-pin or AS-i connecting cable). The signals in question come

from commercially available electronic or electromechanical safety switching devices which monitor the protective equipment of the machine (e.g. emergency stop, light curtain, electrical door switch of a protective enclosure, etc.).

**Note**  
The MS6N-SV-...-E-10V24 must be used in combination with the multi-pin plug socket NECA approved for it. The multi-pin plug socket can be ordered via the modular product system (MP... → 44) or as an accessory (NECA → 56).

**Note**  
To avoid back pressures, it is recommended that the device be operated together with the silencer UOS-1. The silencer can be ordered via the modular product system (SO → 44) or as an accessory (UOS-1 → 58).

**Note**  
Only devices that do not impair the pneumatic protective measure – safe venting – may be placed downstream of the MS6N-SV-...-E. The MS6N-SV-...-E is not permitted for use as a press safety valve.

- Performance level "e"/category 4 according to EN ISO 13849-1
- Conforms to standard IEC 61508
- Switching time delay adjustable via a flow control valve for gradual pressure build-up
- Optional pressure sensor

Safety characteristics		
Type	MS6N-SV-...-E-10V24	MS6N-SV-...-E-ASIS
Conforms to standard	EN ISO 13849-1	
Safety function	Exhausting	
	Avoidance of unexpected start-up (pressurisation)	
Performance level (PL)	Exhausting: up to category 4, PL e	
	Avoidance of unexpected start-up (pressurisation): up to category 4, PL e	
Safety integrity level (SIL)	Exhausting: SIL 3	
	Avoidance of unexpected start-up (pressurisation): SIL 3	
Note on forced dynamisation	Switching frequency min. 1/month	
Certificate issuing authority <sup>1)</sup>	IFA 1001180	TÜV Nord, Registration no. 44 799 12 556236 000
CE marking (see declaration of conformity <sup>1)</sup> )	To EU Machinery Directive	
	To EU EMC Directive	
Shock resistance	Shock test with severity level 2 according to FN 942017-5 and EN 60068-2-27	
Vibration resistance	Transport application test with severity level 2 according to FN 942017-4 and EN 60068-2-6	

1) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

**Note on forced dynamisation: switching frequency min. 1/month**  
The mechanical system is not tested in the controlled (i.e. pressurised) state. If the process-related switching frequency (safe exhausting) is less than once a month, the machine's operator has to carry out a forced switch off.




**Additional functions of MS6N-SV-...-E-ASIS:**

- Integrated pressure sensors via AS-i protocol
- Pressure monitoring (under/over-shooting)

# Soft-start and quick exhaust valves MS6N-SV-E, MS series, NPT

Technical data

Operational principle of the multi-pin plug socket NECA				
Status of enable signal		Status of MS6N-SV-...-E-10V24 with multi-pin plug		
EN1	EN2	NECA-...- MP1	NECA-...- MP3	NECA-...- MP5
0 V	0 V	Unpressurized	MS6N-SV-...-E-10V24 goes into the fault mode.	MS6N-SV-...-E-10V24 does not go into the fault mode, but remains in the safe, unpressurized status. <b>Note:</b> Cross-circuit detection and error detection/evaluation via external controller necessary.
0 V	24 V	MS6N-SV-...-E-10V24 goes into the fault mode.	Pressurized	Pressurized
24 V	24 V	Pressurized	MS6N-SV-...-E-10V24 goes into the fault mode.	MS6N-SV-...-E-10V24 does not go into the fault mode, but remains in the safe, unpressurized status. <b>Note:</b> Cross-circuit detection and error detection/evaluation via external controller necessary.
24 V	0 V	MS6N-SV-...-E-10V24 goes into the fault mode.	Unpressurized	Unpressurized

MS6N-SV-...-E-10V24 with multi-pin plug socket NECA	
NECA-...- MP1	
	
<p>– Static enable signals (EN1 = 24 V, EN2 = 24 V).</p>	
<p>– Clocked enable signals (EN1 = 0 ... 24 V, EN2 = 0 ... 24 V) for cross-circuit detection. Cross-circuit detection with clock signals is in principle carried out by the safety switching device/safety PLC used.</p>	
<p><b>Note</b></p> <p>Given the fact that clock outputs from different controller manufacturers are not standardised, their usability must be checked in each case. If the clock pulse is outside of the described limits, this is recognised by the MS6N-SV-...-E-10V24 as an error and a safe switch-off is performed.</p>	


# Soft-start and quick exhaust valves MS6N-SV-E, MS series, NPT

FESTO

Technical data

## MS6N-SV-...-E-10V24 with multi-pin plug socket NECA


NECA-...-MP3




- Note

The multi-pin plug socket NECA-S1G9-P9-MP3 is intended for conventional circuitry with electromechanical safety relays. If problems arise in use with bipolar semiconductor outputs, use the multi-pin plug socket NECA-S1G9-P9-MP5.

- Static enable signals with opposite potentials.
- The time delay of the level change of the enable signals is monitored.
- Behaviour on detection of a cross circuit:
  - MS6N-SV-...-E-10V24 in the exhausted status: remains in the safe status and goes into the fault mode.
  - MS6N-SV-...-E-10V24 in the pressurized status: goes into the safe status and goes into the fault mode.




NECA-...-MP5



- Note

A cross circuit between the enable signals (EN1/EN2) is not detected and does not cause an error response. The system can be pressurized only when the enable signals are applied correctly.

- Static enable signals with opposite potentials.
- The time delay of the level change of the enable signals is not monitored.
- Behaviour on detection of a cross circuit (through upstream safety switching device/safety PLC):
  - MS6N-SV-...-E-10V24 in the exhausted status: remains in the safe status and does not go into the fault mode.
  - MS6N-SV-...-E-10V24 in the pressurized status: goes into the safe status and does not go into the fault mode.
- Enable signal are galvanically separated from the supply voltage.



- Note

The time delay between EN1 and EN2 must be automatically determined. The duration of the delay is not evaluated.

# Soft-start and quick exhaust valves MS6N-SV-E, MS series, NPT

Technical data

FESTO

## MS6N-SV-...-E-ASIS in the actuator-sensor interface (AS-i)

The actuator-sensor interface (AS-i) is a system for networking sensors and actuators on the lowest level of the automation hierarchy. It is a non-proprietary, open bus system and enables transfer of data and energy on just one line. This simple method permits an efficient configuration with simultaneously reliable performance. The network topology of the AS-i system can be expanded as desired without any difficulty.

An AS-i network consists of a control

unit, a so-called master and the associated sensor and actuator components, namely the slaves. The master cyclically polls all configured slaves and exchanges input and output data with them. A telegram consists of 4 bits of user data. The master communicates with the slaves via a serial transmission protocol.


AS-i Safety at Work is a certified standard that enables safety-related components to be used in the AS-i system. The safe AS-i system is designed

for safety applications up to category 4 according to EN ISO 13849-1 PL "e". Mixed operation of standard components and safety-oriented components is possible. The AS-interface master considers the safety-oriented slaves just like all other slaves and incorporates them into the network. The transmission protocol and the cables in the AS-i system are laid out so that they are also capable of transmitting safety-oriented telegrams.

The AS-i safety monitor is the central

safe component and monitors the safety-oriented slaves assigned to it within an AS-i system. The safety function is ensured via additional signal transmission between the safety-oriented slaves and the AS-i safety monitor. This transmission takes place with a special safety protocol.

In the case of a stop request or defect, the AS-i safety monitor in protection mode reliably switches the system off with a maximum reaction time of 40 ms.



# Soft-start and quick exhaust valves MS6N-SV-E, MS series, NPT

FESTO

Technical data

General technical data	
Pneumatic connection 1, 2	
Female thread	NPT $\frac{1}{2}$
Connecting plate AQ...	NPT $\frac{1}{4}$ , NPT $\frac{3}{8}$ , NPT $\frac{1}{2}$ or NPT $\frac{3}{4}$
Pneumatic connection 3	NPT1
Actuation type	Electric
Design	Piston seat
Type of mounting	Via accessories
	In-line installation
Mounting position	Any
Pressure indicator	Via pressure sensor for displaying output pressure via LCD display and electrical output
	Via pressure gauge for displaying output pressure
	Via pressure gauge with red/green scale for displaying output pressure
	G $\frac{1}{4}$ prepared
Position sensing principle	Solenoid piston principle
Valve function	3/2-way valve, closed, single solenoid
	Soft-start function, adjustable
Non-overlapping	No
Exhaust function	No flow control
Manual override	None
Reset method	Mechanical spring
Type of control	Piloted
Pilot air supply	Internal
Sealing principle	Soft

Flow rate characteristics	
Pneumatic connection	Female thread NPT $\frac{1}{2}$
Standard nominal flow rate $q_{nN}^{1)}$ [l/min]	
In main flow direction 1 $\rightarrow$ 2	4,300
Standard flow rate $q_N$ [l/min], $p_2 = 6$ bar	
In venting direction 2 $\rightarrow$ 3	9,000 <sup>2)</sup>
C value [l/s*min]	
In main flow direction 1 $\rightarrow$ 2	19.3
b value	
In main flow direction 1 $\rightarrow$ 2	0.21

1) Measured at  $p_1 = 6$  bar and  $p_2 = 5$  bar,  $\Delta p = 1$  bar

2) Measured with respect to atmosphere with silencer UOS-1

Electrical data		
Type	MS6N-SV-...-E-10V24	MS6N-SV-...-E-ASIS
Electrical connection	Sub-D, 9-pin	2x M12
Nominal operating voltage [V DC]	24	–
Permissible voltage [%]	$\pm 10$	–
fluctuations		
Operating voltage range for AS-interface [V DC]	–	22 ... 31.6
Duty cycle [%]	100	
Max. switching frequency [Hz]	1	
Switching time off [ms]	40	
Switching time on [ms]	130	
Signal status display	LED and floating contact	LED and via AS-i
Protection class	IP65 with plug socket	

# Soft-start and quick exhaust valves MS6N-SV-E, MS series, NPT

FESTO

Technical data

AS-i Safety-specific data	
Type	MS6N-SV-...-E-ASIS
Fieldbus interface	Socket M12 (AS-i Out) and plug M12 (AS-i In)
LED displays	AS-i and status
Device-specific diagnostics	Inputs for cyclical digital data (exhausted, pressurised, fault) Cyclical analogue values (supply pressure p1, output pressure p2) Acyclical values (counter, pressure monitoring, fault, switching frequency exceeded, status)
Product identification	IO code: 0x7 Profile: 7.5.5 ID code: 0x5 ID1: 0xF ID2: 0x5
Vendor ID AS-interface	0x014D
Device ID AS-interface	0x03A6
Addressing range	Standard slave: 1 ... 31

Operating and environmental conditions		
Type	MS6N-SV-...-E-10V24	MS6N-SV-...-E-ASIS
Operating pressure [bar]	3.5 ... 10	3.5 ... 10
Operating medium	Compressed air according to ISO 8573-1:2010 [7:4:4]	
Note on operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)	
Ambient temperature [°C]	-10 ... +50 (0 ... +50) <sup>1)</sup>	0 ... +50
Temperature of medium [°C]	-10 ... +50 (0 ... +50) <sup>1)</sup>	0 ... +50
Storage temperature [°C]	-10 ... +50 (0 ... +50) <sup>1)</sup>	0 ... +50
Corrosion resistance class CRC <sup>2)</sup>	2	
Noise level [dB(A)]	75 (with silencer UOS-1)	
CE marking (see declaration of conformity) <sup>4)</sup>	To EU EMC Directive <sup>3)</sup> To EU Machinery Directive	
UL certification <sup>4)</sup>	cULus recognized (OL)	
Certification	RCM Mark	
KC marking	KC EMC	

1) With pressure sensor AD...

2) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

3) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: [www.festo.com/sp](http://www.festo.com/sp) → User documentation.

If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

4) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

Weight [g]	
Soft-start and quick exhaust valve	2,000
Soft-start and quick exhaust valve with silencer UOS-1	2,200

Materials	
Housing	Die-cast aluminium
Piston rod	High-alloy stainless steel
Seals	NBR
Note on materials	RoHS-compliant


# Soft-start and quick exhaust valves MS6N-SV-E, MS series, NPT

FESTO

Technical data

## Switching point

Pressure p as a function of time t



Note


The +20%/–10% switching point tolerance refers to the operating pressure p1.  
Example: A switching point from 1.6 bar to 2.8 bar is permissible at an operating pressure of 4 bar.

## Dimensions – Basic design

With supply voltage 10V24,  
with female thread NPT $\frac{1}{2}$ , with cover plate

Download CAD data → [www.festo.com](http://www.festo.com)

With supply voltage ASIS,  
with female thread NPT $\frac{1}{2}$ , with cover plate



1 Regulating screw for flow control valve

2 Silencer UOS-1

3 Multi-pin plug socket NECA or AS-i configuration plug CACC

4 Dimension without cable

5 Adapter AD

6 M12 socket, 5-pin

7 M12 pin, 5-pin

→ Flow direction

Type	B1	B2	B3	B4	D1	D5	D6	L1	L2	L3	L4
MS6N-SV- $\frac{1}{2}$ -E-10V24	62	59	104	23	NPT $\frac{1}{2}$	NPT1	55	228	81	61	174
MS6N-SV- $\frac{1}{2}$ -E-ASIS				26						28	



# Soft-start and quick exhaust valves MS6N-SV-E, MS series, NPT

FESTO


Technical data

## Dimensions – Pressure gauge/pressure gauge alternatives

Download CAD data → [www.festo.com](http://www.festo.com)

Integrated MS pressure gauge with standard scale AG or red/green scale RG

Adapter plate A4 for EN pressure gauge 1/4, without pressure gauge




Type	B2	B3	D4
MS6N-SV-...-E-...-AG	59	105	–
MS6N-SV-...-E-...-RG	59	106.5	–
MS6N-SV-...-E-...-A4	59	106.5	G1/4

## Dimensions – Pressure gauge/pressure gauge alternatives

Download CAD data → [www.festo.com](http://www.festo.com)

Pressure sensor with LCD display AD1 ... AD4

Technical data → Internet: [sde1](http://sde1.festo.com)



Type	B2	B3	D6	L5	L6
MS6N-SV-...-E-...-AD1/AD2	59	131	M8x1	31.2	46.7
MS6N-SV-...-E-...-AD3/AD4			M12x1		55.8

# Soft-start and quick exhaust valves MS6N-SV-E, MS series, NPT

FESTO

Ordering data – Modular products

M Mandatory data →							
Module No.	Series	Size	Thread	Function	Pneumatic connection	Performance level	Supply voltage
548714	MS	6	N	SV	1/2, AQ...	E	10V24, ASIS
Ordering example							
548714	MS	6	N	- SV	- AQP	- E	- 10V24 -

Ordering table					
Grid dimension	[mm]	62	Condi- tions	Code	Enter code
M Module No.	548714				
Series	Standard			MS	MS
Size	6			6	6
Thread	NPT thread			N	N
Function	Soft-start and quick exhaust valve			-SV	-SV
Pneumatic connection	Female thread NPT1/2			-1/2	
	Connecting plate NPT1/4			-AQN	
	Connecting plate NPT3/8			-AQP	
	Connecting plate NPT1/2			-AQR	
	Connecting plate NPT3/4			-AQS	
Performance level	Category 4, 2-channel with self-monitoring, to EN ISO 13849-1			-E	-E
Supply voltage	24 V DC			-10V24	
	22 ... 31.6 V DC, AS-i Safety at Work, SPEC3.0 Profile 7.5.5			-ASIS	

Transfer order code

548714	MS	6	N	- SV	-	E	-
--------	----	---	---	------	---	---	---

# Soft-start and quick exhaust valves MS6N-SV-E, MS series, NPT

FESTO

Ordering data – Modular products

Options						
Silencer	Pressure gauge/ pressure gauge alternatives	Alternative pres- sure gauge scale	Multi-pin plug socket	Type of mounting	UL certification	Flow direction
SO	AG, A4, RG, AD1 ... AD4	BAR, MPA	MP1, MP3, MP5	WPB	UL1	Z
- SO	- AG	-	- MP1	- WPB	-	-

Ordering table						
Grid dimension	[mm]	62	Condi- tions	Code		Enter code
0 Silencer		Open silencer		-SO		
Pressure gauge/pressure gauge alternatives		MS pressure gauge	1	-AG		
		Adapter plate for EN pressure gauge 1/4, without pressure gauge	2	-A4		
		Integrated pressure gauge, red/green scale	1	-RG		
		Pressure sensor with LCD display, plug M8, 1 switching output PNP, 3-pin	2	-AD1		
		Pressure sensor with LCD display, plug M8, 1 switching output NPN, 3-pin	2	-AD2		
		Pressure sensor with LCD display, plug M12, 1 switching output PNP, 4-pin, analogue output 4 ... 20 mA	2	-AD3		
		Pressure sensor with LCD display, plug M12, 1 switching output NPN, 4-pin, analogue output 4 ... 20 mA	2	-AD4		
Alternative pressure gauge scale		bar	3	-BAR		
		MPa	3	-MPA		
Multi-pin plug socket		Sub-D, 9-pin, screw terminal, without cable, static enable signals (EN1 = 24 V, EN2 = 24 V)	2	-MP1		
		Sub-D, 9-pin, screw terminal, without cable, static enable signals (EN1 = 0 V, EN2 = 24 V), short-circuit detection possible	2	-MP3		
		Sub-D, 9-pin, screw terminal, without cable, static enable signals (EN1 = 0 V, EN2 = 24 V), galvanic isolation of the enable signals from the supply voltage	2	-MP5		
Type of mounting		Mounting bracket for large wall gap		-WPB		
UL certification		cULus, ordinary location for Canada and USA	2	-UL1		
Flow direction		Flow direction from right to left		-Z		

- 1 AG, RG Pressure gauge scale in psi.  
With pressure gauge RG: PSI scale serves only as an auxiliary scale (inner scale),  
outer scale in bar
- 2 A4, AD1, AD2, AD3, AD4, MP1, MP3, MP5, UL1  
Not with supply voltage ASIS
- 3 BAR, MPA Only in combination with pressure gauge AG or RG

Transfer order code

- [ ] - [ ] - [ ] - [ ] - [ ] - [ ] - [ ]

## Soft-start and quick exhaust valves MS-SV, MS series, NPT

FESTO

Accessories

### Multi-pin plug socket NECA

(order code in the modular product system: MP1/MP3/MP5)

- For soft-start and quick exhaust valve MS6N-SV-E-10V24



Technical data		
Type of mounting		Via through-hole
Electrical connection 1		Sub-D 9-pin
Electrical connection 2		Screw terminal 9-pin
Operating voltage range	[V DC]	21.6 ... 26.4
Nominal operating voltage	[V DC]	24
Acceptable current load	[A]	1.0
Connection cross section	[mm <sup>2</sup> ]	0.34 ... 1.0 without wire end sleeves
	[mm <sup>2</sup> ]	0.34 ... 0.5 with wire end sleeves
Permissible cable diameter	[mm]	5.0 ... 10.0
Protection class to IEC 60529		IP65

Operating and environmental conditions		
Relative air humidity		95%, non-condensing
Ambient temperature	[°C]	0 ... +50
Storage temperature	[°C]	-20 ... +70
Corrosion resistance class CRC <sup>1)</sup>		2

- 1) Corrosion resistance class CRC 2 to Festo standard FN 940070  
Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

Materials	
Housing	PA reinforced
Screws	Steel
Union nut	Brass
Seals	NBR


# Soft-start and quick exhaust valves MS-SV, MS series, NPT

Accessories

**FESTO**

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



B1	H1	L1	L2
61	20	61	54.1

## Ordering data

Description	Connection	Weight [g]	Part No.	Type
For MS6N-SV-E-10V24	Without cable, static enable signals (EN1 = 24 V, EN2 = 24 V)	60	<b>548719</b>	<b>NECA-S1G9-P9-MP1</b>
	Without cable, static enable signals (EN1 = 0 V, EN2 = 24 V), cross-circuit detection possible	60	<b>552703</b>	<b>NECA-S1G9-P9-MP3</b>
	Without cable, static enable signals (EN1 = 0 V, EN2 = 24 V), galvanic isolation of the enable signals from the supply voltage	60	<b>573695</b>	<b>NECA-S1G9-P9-MP5</b>

## Soft-start and quick exhaust valves MS-SV, MS series, NPT

FESTO

Accessories

### Silencer UOS-1

(order code in the modular product system: S0)

- For soft-start and quick exhaust valve MS6N-SV-D/E

### Silencer UOS-1-LF

- For soft-start and quick exhaust valve MS6N-SV-D/E



Note

The space-saving silencer UOS-1-LF may only be used for applications with low exhaust rates. Pneumatic port 2 at the soft-start and quick exhaust valve MS6N-SV-D/E must be reduced to NPT $\frac{1}{4}$  using a connecting plate MS6-AQN.



UOS-1



UOS-1-LF



Technical data	
Pneumatic connection	G1
Design	Open silencer
Type of mounting	Via male thread
Mounting position	Any
Type of seal on threaded collar	No seal

Operating and environmental conditions	
Operating pressure [bar]	0 ... 10
Operating medium	Compressed air to ISO 8573-1:2010 [–:–:–]
Ambient temperature [°C]	–10 ... +50
Corrosion resistance class CRC <sup>1)</sup>	2

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

Materials		
Type	UOS-1	UOS-1-LF
Housing	POM	Wrought aluminium alloy
Sleeve	Wrought aluminium alloy	–
Silencer insert	PE	
Note on materials	RoHS-compliant	
	Free of copper and PTFE	

Dimensions		Download CAD data → <a href="http://www.festo.com">www.festo.com</a>		
Type	UOS-1	UOS-1-LF		
				

Type	D1	D2	L1	L2
UOS-1	G1	55	156.5	11.5
UOS-1-LF			72.2	13

Ordering data		Weight [g]	Part No.	Type
For MS6N-SV-D/E	For high exhaust rate	200	552252	UOS-1
	For low exhaust rate	157.9	1901207	UOS-1-LF

## Soft-start and quick exhaust valves MS-SV, MS series, NPT


FESTO

Accessories

### AS-i configuration plug CACC

- For soft-start and quick exhaust valve MS6N-SV-E-ASIS

Note on materials: RoHS-compliant



Dimensions and ordering data					
Description	D1	L1	≈G1	Part No.	Type
For MS6N-SV-E-ASIS	14.5	48.3	13	573923	CACC-CP-AS

### Cover MS-SV-MK

(order code in the modular product system: MK)

- For soft-start and quick exhaust valve MS6N-SV-C

Note on materials: RoHS-compliant




Ordering data			
Description		CRC <sup>1)</sup>	Part No. Type
For MS6N-SV-C	Tamper protection for manual override at the soft-start and quick exhaust valve, flow control screw, adjusting screw for pressure switchover point and manual override at the pilot solenoid valve	2	8001479 MS6-SV-C-MK


1) Corrosion resistance class CRC 2 to Festo standard FN 940070  
Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.



## Soft-start and quick exhaust valves MS-SV, MS series, NPT


**FESTO**


Accessories


Ordering data – Adapter AD					
	Description	Pneumatic connection		Part No.	Type
		1	2		
	For MS6N-SV-E	NPT1	G1	<b>546547</b>	<b>AD-1NPT-G1-I</b>

Ordering data – Silencer U-...-B				Technical data → Internet: u	
	Description	Pneumatic connection	Order code in the modular product system	Part No.	Type
	For MS6N-SV-C	NPT3/4	S	<b>566823</b>	<b>U-3/4-B-NPT</b>

Ordering data – Proximity sensor SMT							Technical data → Internet: smt	
	Description	Switching output	Switching element function	Electrical connection	Cable length [m]	Order code in the modular product system	Part No.	Type
	For MS6N-SV-D	PNP	N/O contact	Cable with plug M8x1, 3-pin	0.3	2M8/S3	★ <b>574334</b>	<b>SMT-8M-A-PS-24V-E-0,3-M8D</b>
				Cable with plug M12x1, 3-pin	0.3	2M12/S3	★ <b>574337</b>	<b>SMT-8M-A-PS-24V-E-0,3-M12</b>
	For MS6N-SV-D	PNP	N/O contact	Cable, 3-wire	5	20E/S3	★ <b>574336</b>	<b>SMT-8M-A-PS-24V-E-5,0-OE</b>

Ordering data – Plug socket MSSD				Technical data → Internet: mssd	
	Description	Electrical connection	Type of mounting for cable connection	Part No.	Type
	For MS6N-SV-C/D	3-pin	Clamping screws	★ <b>151687</b>	<b>MSSD-EB</b>
		4-pin	Insulation displacement connectors	<b>192745</b>	<b>MSSD-EB-S-M14</b>
		3-pin	Clamping screws	<b>539712</b>	<b>MSSD-EB-M12</b>

Ordering data – Plug socket with cable KMEB						Technical data → Internet: kmeb	
	Description	Operating voltage	Electrical connection	Switching status display	Cable length [m]	Part No.	Type
	For MS6N-SV-C/D	24 V DC	2-pin	LED	2.5	<b>547268</b>	<b>KMEB-3-24-2,5-LED</b>
					5	<b>547269</b>	<b>KMEB-3-24-5-LED</b>
				–	2.5	<b>547270</b>	<b>KMEB-3-24-2,5</b>
			3-pin		5	<b>547271</b>	<b>KMEB-3-24-5</b>
				LED	2.5	★ <b>151688</b>	<b>KMEB-1-24-2,5-LED</b>
					5	<b>151689</b>	<b>KMEB-1-24-5-LED</b>
					10	<b>193457</b>	<b>KMEB-1-24-10-LED</b>
		230 V AC	3-pin	–	2.5	<b>151690</b>	<b>KMEB-1-230AC-2,5</b>
					5	<b>151691</b>	<b>KMEB-1-230AC-5</b>

Ordering data – Illuminating seal MEB-LD			Technical data → Internet: meb	
	Description	Operating voltage range	Part No.	Type
	For plug socket with cable KMEB and plug socket MSSD-EB	12 ... 24 V DC	<b>151717</b>	<b>MEB-LD-12-24DC</b>
		230 V DC/AC ±10%	<b>151718</b>	<b>MEB-LD-230AC</b>

Festo core product range



- ★ Ready for dispatch from the Festo factory in 24 hours
- ★ Ready for dispatch in 5 days maximum from stock






## Soft-start and quick exhaust valves MS-SV, MS series, NPT

**FESTO**

Accessories

Ordering data – Connecting cable NEBU-M8				Technical data → Internet: nebu	
	Electrical connection	Number of wires	Cable length [m]	Part No.	Type
	M8x1, straight socket	3	2.5	★ 541333	NEBU-M8G3-K-2.5-LE3
			5	★ 541334	NEBU-M8G3-K-5-LE3
	M8x1, angled socket	3	2.5	★ 541338	NEBU-M8W3-K-2.5-LE3
			5	★ 541341	NEBU-M8W3-K-5-LE3

Ordering data – Connecting cable NEBU-M12				Technical data → Internet: nebu	
	Electrical connection	Number of wires	Cable length [m]	Part No.	Type
	M12x1, straight socket	4	2.5	★ 550326	NEBU-M12G5-K-2.5-LE4
			5	★ 541328	NEBU-M12G5-K-5-LE4
	M12x1, angled socket	4	2.5	550325	NEBU-M12W5-K-2.5-LE4
			5	541329	NEBU-M12W5-K-5-LE4

Ordering data – Pressure gauge MA					
	Nominal size	Pneumatic connection	Display range		Part No. Type
			[bar]	[psi]	
	Pressure gauge MA, EN 837-1				
	40	R $\frac{1}{4}$	0 ... 16	0 ... 232	187080 MA-40-16-R $\frac{1}{4}$ -EN
		G $\frac{1}{4}$	0 ... 16	0 ... 232	183901 MA-40-16-G $\frac{1}{4}$ -EN
	Pressure gauge MA, EN 837-1, with red/green range				
	50	R $\frac{1}{4}$	0 ... 16	–	525729 MA-50-16-R $\frac{1}{4}$ -E-RG

Festo core product range

- ★ Ready for dispatch from the Festo factory in 24 hours
- ☆ Ready for dispatch in 5 days maximum from stock

# Festo - Your Partner in Automation



**1 Festo Inc.**  
5300 Explorer Drive  
Mississauga, ON L4W 5G4  
Canada

**Festo Customer Interaction Center**  
Tel: 1 877 463 3786  
Fax: 1 877 393 3786  
Email: [customer.service.ca@festo.com](mailto:customer.service.ca@festo.com)



**2 Festo Pneumatic**  
Av. Ceylán 3,  
Col. Tequesquináhuac  
54020 Tlalnepantla,  
Estado de México

**Multinational Contact Center**  
01 800 337 8669  
[ventas.mexico@festo.com](mailto:ventas.mexico@festo.com)



**3 Festo Corporation**  
1377 Motor Parkway  
Suite 310  
Islandia, NY 11749

**Festo Customer Interaction Center**  
1 800 993 3786  
1 800 963 3786  
[customer.service.us@festo.com](mailto:customer.service.us@festo.com)



**4 Regional Service Center**  
7777 Columbia Road  
Mason, OH 45040

Connect with us

[f](#) [t](#) [in](#) [You Tube](#)

[www.festo.com/socialmedia](http://www.festo.com/socialmedia)



[www.festo.com](http://www.festo.com)

Subject to change