

AS-interface® components


**FESTO**



# AS-interface® components

Overview of AS-interface

FESTO



# AS-interface® components

Overview of AS-interface

FESTO

## Basic principles and features of the bus system

### Introduction

AS-interface is a non-proprietary, open installation system with a large and growing share of the market at the lowest level of the decentralised production and process automation hierarchy.

The non-proprietary and open characteristics of the system are guaranteed by the European standard EN 50295 and the international

standard IEC 62026-2. Certified products bear the logo of the AS-International Association.

The AS-International Association and its affiliated organisations represent the interests of all manufacturers with an interest in the AS-interface.

### Design

The AS-interface system permits the transfer of power and data using a single cable. The advanced technology used to connect stations to the yellow cable and the low connection costs mean that even stations with a small number of inputs and outputs (max. 8 inputs and 8 outputs per valve terminal with two chips) can be networked. Reductions in installation costs of between 26% and 40% have been demonstrated depending on the system type. This solution is an ideal low-cost option for connecting individual or

small groups of actuators, valves and sensors to a master controller. New developments as per Specification V2.1 published at the start of 2000 such as the parameterisable profile 7.4 or the AS-interface Safety at Work concept opened the way for new areas of application and facilitated considerably more efficient installation and networking concepts in many instances.

Specification V3.0 published in 2005 represents another giant leap forward, facilitating convenient activation of

analogue I/O, complex slaves or serial text and data transfer, for example.

- Slaves as per Specifications V2.0 and V2.1 will also run under V3.0 – the system is fully downwards compatible. Benefits of AS-interface Specification V3.0:
- All of the benefits of the simple installation system since Specification V2.0 are retained
- Up to 400% more I/Os per master
- Improved peripheral error diagnostics
- More functions within Specifications V2.1 and V3.0, e.g. easy integration of complex 16-bit slaves,

fast analogue modules, DTM integration, asynchronous serial protocol, safety slaves

- Slave profiles for specific functions as well as interchangeability. Mix of different vendors and products, e.g. for parameters or communication services

AS-interface with A/B mode gives you 100% more. In A/B mode, each slave address is used twice. An output bit is used for A/B address differentiation (see table for case distinctions). The cycle time for pneumatic chains is generally more than adequate.

| Specification Version | Inputs | Outputs | Bus cycle (ms) | No. of slaves, digital | No. of slaves, analogue | Σ I/O |
|-----------------------|--------|---------|----------------|------------------------|-------------------------|-------|
| 2.0                   | 4/4    | 4       | 5              | 31                     | 31                      | 248   |
| 2.1                   | 4      | 3       | 10             | 62                     | 31                      | 434   |
| 3.0                   | 4/8    | 4/8     | 20             | 62                     | 62                      | 992   |

### Master-slave principle

- Non-proprietary
- No restrictions in terms of cable layout and/or topology
- Data and power via a single two-wire cable
- Immune to interference
- Medium: unscreened cable 2x 1.5 mm<sup>2</sup>
- With 31 slaves, max. 4 inputs and 4 outputs per slave
- Data and power supply for up to 8 outputs per AS-interface string

- With 62 slaves, max. 4 inputs and 3 outputs per slave (A/B mode as per Specification V2.1)
- Modules for control cabinets (IP20) and harsh industrial environments (IP65, IP67)
- With 31 slaves, 4 analogue inputs or outputs per slave
- Profile 7.3: analogue values (16 bits) per slave (as per Specification V2.1)

- Profile 7.4: parameterisable communication profile, e.g. 16x 16 bits per slave (as per Specification V2.1)
- Profile 7.A.7 allows 4 bits for digital inputs and 4 bits for digital outputs on just one A/B slave. The 4 outputs are transmitted in two A/B bus cycles of 2 bits each. This extends the cycle time (in the worst-case scenario) to 20 ms.

- Insulation displacement technology
- Cable length 100 m, can be extended to up to 200 m through the use of an extension plug and to up to 500 m through the use of repeaters, etc.
- Highly effective error control
- Simple commissioning
- Electronic address selection via the bus connection



Note

Slaves to Specification V3.0 require a master to Specification V3.0.

# AS-interface® components

Overview of AS-interface

FESTO

## Basic features

### Simple connection technology

- One cable for power and data
- Cable profile prevents polarity reversal
- Error control means there is no need for screening
- Insulation displacement connection technology guarantees Festo plug and work
- Alternative bus connection technology M12, 4-pin (standardised)

### Ideal for pneumatic applications

- Local control of small groups of actuators or individual distributed actuators covering an extensive area with
- short tubing lengths,
  - high cycle rates,
  - low air consumption.
- Installation and communication are carried out via AS-interface components.

### A powerful system component

AS-interface is clearly subordinate to the fieldbuses already in use and is therefore less a competing product and more a technically necessary and economically advisable add-on.

### Everything from a single source

- Festo is your single source for the AS-interface. This means
- one contact person,
  - competent solutions from the market leader,
  - convenient ordering system,
  - complete delivery service,
  - co-ordinated solutions for motion and control,
  - worldwide service round the clock.

## Optimised cycle rates

Decentralised solutions at the AS-interface permit optimised electro-pneumatic control loop systems: valve response times and optimum pairings of cylinder diameter and stroke save up to

- 20% cycle time with standard components
- 30% cycle time with fast switching valves
- 40% installation costs
- 50% air consumption/flow rate

## Product range overview


### Valves

- Integrated inputs on valve terminals CPV, MPA-S and VTSA/VTSA-F
- More inputs thanks to 4-fold and 8-fold input modules
- On request: Application-specific valves and integration solutions


### Gateways

- AS-interface gateways CESA as master within the AS-interface network and slave within a fieldbus network.
- PROFIBUS
  - CANopen

## Components



## Application examples



### Sorting

Valve terminals MPA-S, VTSA/VTSA-F and CPV:  
Compact Performance is synonymous with high performance and low


weight. Mounting close to the drives simplifies installation, saves compressed air and increases the cycle rates.



### Conveyor technology

Individually distributed drives and sensors covering an extensive area are common features of conveyor systems. The AS-interface is particularly suited to systems of this type.


Compact I/O modules support the direct connection of one or two valves of any size and up to 4 sensors to the AS-interface.



### Packaging

More complex machines frequently require decentralised installation concepts within the system in order to achieve an efficient electrical installation.

The AS-interface controls complex modules and upstream functions such as packaging in this picture.



### Assembling

Assembly, moving, handling: this often means rapid-fire sequences, tight installation spaces and the need for reduced weight.

Compact I/O modules, valve terminals and matching drives provide the optimum solution here.



### Process engineering

Water treatment  
Automation and decentralised intelligence are innovative features of newer systems.  
A compact I/O module is suitable for all valves with Namur interface. The


VTSA/VTSA-F valve terminal provides new scope for flow processes in 24-hour non-stop mode. Vertical pressure shut-off plates enable valve replacement under pressure (hot-swap) and thus avoid downtime.

# AS-interface® components

System overview

FESTO

## Master



AS-interface gateways are used to connect the AS-interface network to a higher-level fieldbus. They behave like a master within the AS-interface network and a slave within the fieldbus network.

AS-interface gateways from Festo conform to the AS-interface Specification 3.0 and support the extended addressing range with up to 62 AS-interface slaves.

Versions


- CANopen
- PROFIBUS

## Slaves

### Valves

- Simple solution incorporating compact EA modules
- Integrated inputs on valve terminals CPV, MPA-S and VTSA/VTSA-F
- More inputs thanks to 4-fold and 8-fold input modules
- On request: Application-specific valves and integration solutions


## Accessories



- Addressing device with user-friendly operating and diagnostic functions for the entire AS-interface, for example to perform the following tasks in a fully installed network:
  - change addresses
  - set outputs
  - read inputs
  - and many more
- Power supply unit for AS-interface
- Primary switched mode modular power supply
- Compact, modular and energy-saving power supply system for AS-interface – with integrated earth-fault monitoring system. Load: 5 or 10 A
- Installation accessories for installing the flat cable

## Valve interface variants

### Bus node CTEU




Incorporation of a range of valve terminals with I-Port interface in the AS-Interface:

- VTUG
- CPV

- VTUB-12
- VTOC
- MPA-L
- Universal connection technology M12

- Optional decentralised installation of the bus node with electrical connection box CAPC
- Basic diagnostics: undervoltage, short circuit

### Compact valve terminal CPV




Maximum performance of 400 ... 1600 l/min with minimal space requirement

- Valve combinations of 2, 4 or 8 valve slices
- Vacuum generation, relays and more in one unit

- Smart tubing system via pneumatic multiple connector plate:
  - Rapid replacement of valve terminals
  - With control cabinet installation: no internal tubing required

- M8 inputs included for each valve position
- Ex Zone 2, 22
- ASI Specification V2.0, V2.1 or V3.0

### Modular, multi-functional valve terminal MPA-S




- Valves on a sub-base: individual valves can be easily replaced
- MPA-S: sturdy and modular from 360 ... 700 l/min
- Flexible valve combinations for 2 ... 8 solenoid coils
- Valve terminals can be expanded at a later date

- Mix of MPA1/2 on a valve terminal possible for optimised flow rates and control loop systems
- All valve functions, regulators and pressure gauges for variable pressure adjustment per valve position.
- 4 or 8 inputs with selectable connection technology

- Selectable connection technology on the bus. Flat cable in the case of the 4E4A version or M12 round cable in the case of the 4E4A and 8E8A versions (where 'E' stands for inputs and 'A' outputs)

### Modular, multi-functional valve terminal VTSA/VTSA-F




- Standard valves 18, 26, 42 and 52 mm to ISO 17504-2 and 5599-2 on a sub-base: individual valves can be easily switched
- VTSA/VTSA-F: compact and modular from 550 ... 1500 l/min
- Flexible valve combinations for 1 ... 8 solenoid coils
- Valve terminals can be expanded at a later date

- Mix of 3 valve sizes on a valve terminal possible for optimised flow rates and control loop systems
- All valve functions, multiple pressure zones, regulators and pressure gauges for precision pressure adjustment per valve position, flow control, pressure shut-off plates for valve replacement under pressure (hot-swap) and additional components for vertical stacking

- 4 or 8 inputs with selectable connection technology
- Selectable connection technology on the bus. Flat cable in the case of the 4E4A version or M12 round cable in the case of the 4E4A and 8E8A versions (where 'E' stands for inputs and 'A' outputs)

### Compact I/O modules, valve interfaces



- Highly compact modules
- Sturdy, encapsulated electrics
- Bus and auxiliary power supply 2x M12 looped through


- Inputs 200 mA
- Outputs 1 A

- 8 inputs M8
- 4 inputs and 3 outputs M12

## AS-interface® components

CESA AS-interface modules

FESTO



### CESA AS-interface modules

AS-interface gateways are an ideal way of connecting decentralised AS-interface networks to higher-level controllers via a fieldbus. They enable system parts to be set up decentrally and combined into logical units.

#### General

- Extended AS-interface diagnostic functions
- Simple configuration error history
- Error counters for monitoring the quality of data communication on the AS-interface cable

#### Versions

- PROFIBUS and CANopen
- Extended addressing range, up to 62 AS-interface slaves
- Terminal strip connection technology
- LCD display and LEDs
- Conforms to AS-interface Specification 3.0

#### Application

- Interface between centralised controller with fieldbus interface and valve terminals and input/outputs with AS-i interface


# AS-interface® components

CESA AS-interface modules – Connection technology and addressing

FESTO

## Handling


### Operation



The AS-interface gateways can be configured and programmed using the GSPF software.


An alternative option for programming, commissioning or troubleshooting is to use the operating buttons on the gateway and the LED and LCD displays on the gateway.

### AS-interface connections



The AS-interface network as well as the power supply for the gateway and AS-interface are connected via a terminal strip.

## Mounting



The gateway is mounted using an H-rail.

There are appropriate lugs on the rear of the device.

### Extended addressing range

The extended addressing range enables a total of 62 slaves to be operated on an AS-interface master. The masters as well as the slaves must be designed for the extended addressing range in order to be able to exploit the full number of slaves.

With the extended addressing range, two slaves share one address. Standard slaves do not have this capability. They can be connected to a master

with an extended addressing range, but also occupy a full address. In other words, up to 62 slaves with an extended addressing range but only 31 standard slaves can be connected to a master with an extended addressing range.

Slaves with an extended addressing range can, like standard slaves, be connected to a standard master, but must be configured as an "A" slave.

# AS-interface® components

CESA AS-interface modules

FESTO

| General technical data  |        |                                                     |               |
|-------------------------|--------|-----------------------------------------------------|---------------|
|                         |        | CESA-GW-AS-PB                                       | CESA-GW-AS-CO |
| Operating elements      |        | 4 buttons                                           |               |
| Status displays         |        | LCD display                                         |               |
|                         |        | Yellow LED: Projection mode                         |               |
|                         |        | Green LED: AS-interface operating normally          |               |
|                         |        | Green LED: AS-interface voltage OK                  |               |
|                         |        | Green LED: PROFIBUS master detected                 |               |
|                         |        | Green LED: Slave programming                        |               |
|                         |        | Green LED: Voltage ON                               |               |
|                         |        | Red LED: Configuration error                        |               |
| Operating voltage       | [V DC] | 30 (AS-interface voltage)                           |               |
| Current consumption     | [mA]   | 200 (from the AS-interface circuit)                 |               |
| Protection class        |        | IP20                                                |               |
| Resistance to shock     |        | As per EN 61131-2                                   |               |
| Resistance to vibration |        | As per EN 61131-2                                   |               |
| Product weight          | [g]    | 460                                                 | 520           |
| Dimensions W x L x H    | [mm]   | 75 x 120 x 83                                       | 85 x 120 x 83 |
| Materials               |        |                                                     |               |
| Housing                 |        | High-alloy stainless steel                          |               |
| Note on materials       |        | Contains PWIS (paint-wetting impairment substances) |               |
|                         |        | RoHS-compliant                                      |               |

| Technical data – Interfaces      |  |                              |                                          |
|----------------------------------|--|------------------------------|------------------------------------------|
|                                  |  | CESA-GW-AS-PB                | CESA-GW-AS-CO                            |
| Fieldbus interface               |  |                              |                                          |
| Type                             |  | PROFIBUS to DIN 19245 Part 3 | CANopen, Device Specification CiA DS-301 |
| Connection technology            |  | Sub-D socket, 9-pin          | COMBICON plug, 5-pin                     |
| Transmission rate                |  | 9.6 kbps ... 12 Mbps         | 10 kbps ... 1 Mbps                       |
| Programming/diagnostic interface |  |                              |                                          |
| Type                             |  | RS 232 serial interface      |                                          |

| Operating and environmental conditions                |      |                     |               |
|-------------------------------------------------------|------|---------------------|---------------|
|                                                       |      | CESA-GW-AS-PB       | CESA-GW-AS-CO |
| Ambient temperature                                   | [°C] | 0 ... +55           |               |
| Storage temperature                                   | [°C] | -25 ... +85         |               |
| Certification                                         |      | cULus listed (OL)   |               |
|                                                       |      | C-Tick              |               |
| CE mark (see declaration of conformity) <sup>1)</sup> |      | To EU EMC Directive |               |


1) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: [www.festo.com/sp](http://www.festo.com/sp) → Certificates.  
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

# AS-interface® components

CESA AS-interface modules – Connections



## Connection and display components



### Pin allocation – PROFIBUS

|                           | Pin | Signal    | Meaning                        |
|---------------------------|-----|-----------|--------------------------------|
| Sub-D socket to DIN 50170 |     |           |                                |
|                           | 1   | n.c.      | Not connected                  |
|                           | 2   | n.c.      | Not connected                  |
|                           | 3   | RxD/TxD-P | Data transmission line B       |
|                           | 4   | n.c.      | Not connected                  |
|                           | 5   | DGND      | Data reference potential (0 V) |
|                           | 6   | VP        | Supply voltage (+5 V)          |
|                           | 7   | n.c.      | Not connected                  |
|                           | 8   | RxD/TxD-N | Data transmission line A       |
|                           | 9   | n.c.      | Not connected                  |



### Pin allocation – CANopen

|                                     | Pin | Signal   | Meaning                             |
|-------------------------------------|-----|----------|-------------------------------------|
| Terminal strip, 5-pin <sup>1)</sup> |     |          |                                     |
|                                     | 1   | V+       | 24 V DC supply CAN interface        |
|                                     | 2   | CAN_H    | Received/transmitted data high      |
|                                     | 3   | Screened | Connection to FE (functional earth) |
|                                     | 4   | CAN_L    | Received/transmitted data low       |
|                                     | 5   | V-       | 0 V CAN interface                   |

1) The interface is supplied with voltage via the plug.

### Pin allocation – AS-interface





|                                                                                     | Signal | Meaning    |                                            |
|-------------------------------------------------------------------------------------|--------|------------|--------------------------------------------|
| Screw terminal                                                                      |        |            |                                            |
|  | 1      | +AS-i-     | Connection to AS-i circuit                 |
|                                                                                     | 2      | AS-i +PWR- | Supply voltage for AS-i circuit (max. 8 A) |
|                                                                                     | 3      | FE         | Functional earth                           |

| Dimensions                                                                         |    |    |     |     |    |    | Download CAD data → <a href="http://www.festo.com">www.festo.com</a>                |  |
|------------------------------------------------------------------------------------|----|----|-----|-----|----|----|-------------------------------------------------------------------------------------|--|
| CESA-GW-AS-PB                                                                      |    |    |     |     |    |    | CESA-GW-AS-CO                                                                       |  |
|  |    |    |     |     |    |    |  |  |
| Type                                                                               | B1 | B2 | H1  | H2  | L1 | L2 |                                                                                     |  |
| CESA-GW-AS-PB                                                                      | 76 | 7  | 125 | 120 | 75 | 55 |                                                                                     |  |
| CESA-GW-AS-CO                                                                      | 76 | 7  | 125 | 120 | 85 | 55 |                                                                                     |  |

# AS-interface® components

CESA AS-interface modules – Accessories

**FESTO**

| Ordering data                                                                       |                                                                                             |  |       |         | Part No.          | Type |
|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------|--|-------|---------|-------------------|------|
| AS-interface gateway                                                                |                                                                                             |  |       |         |                   |      |
|    | AS-interface master with PROFIBUS DP fieldbus connection                                    |  |       | 567032  | CESA-GW-AS-PB     |      |
|                                                                                     | AS-interface master with CANopen fieldbus connection                                        |  |       | 567033  | CESA-GW-AS-CO     |      |
| PROFIBUS bus connection                                                             |                                                                                             |  |       |         |                   |      |
|    | Sub-D plug, angled                                                                          |  |       | 533780  | FBS-SUB-9-WS-PB-K |      |
| AS-interface                                                                        |                                                                                             |  |       |         |                   |      |
|    | AS-interface flat cable, yellow                                                             |  | 100 m | 18940   | KASI-1,5-Y-100    |      |
|                                                                                     | AS-interface flat cable, black                                                              |  | 100 m | 18941   | KASI-1,5-Z-100    |      |
|   | Cable cap for flat cable (pack of 50)                                                       |  |       | 18787   | ASI-KK-FK         |      |
|  | Cable sleeve (pack of 20)                                                                   |  |       | 165593  | ASI-KT-FK         |      |
|  | AS-interface module as bus termination                                                      |  |       | 567035  | CACF-BT-AS        |      |
|  | Primary switched mode, modular power supply<br>24 V DC power supply                         |  | 5 A   | 2247681 | CACN-3A-1-5       |      |
|                                                                                     |                                                                                             |  | 10 A  | 2247682 | CACN-3A-1-10      |      |
|  | H-rail to EN 60715                                                                          |  |       | 35430   | NRH-35-2000       |      |
|  | Software for configuring the system and diagnosing the AS-interface slaves during servicing |  |       | 567036  | GSPF-BS-1-AF-ML   |      |



## Interface module CTEU-AS

The bus node manages communication between the valve terminal and a higher-order AS-Interface® master.

### General

The module has a system and load supply, a bus connection and a connection to the valve terminal with serial I-Port interface.

### Versions

The module has basic diagnostic functions. It has 3 integrated LEDs for on-site display. A maximum of 2 byte inputs and 2 byte outputs are transmitted in the cyclic process image.

### Application


- Activation of up to 16 solenoid coils per valve terminal
- Automatic addressing
- Automatic detection of the number of connected valves

# AS-Interface® components

Bus node CTEU-AS

FESTO

## System overview



- Communication with the higher-order controller via fieldbus
- Use a bus node CTEU that is compatible with the fieldbus protocol
- Up to 24 valve positions (depending on the valve terminal)
- Flow rate of up to 1200 l/min (depending on the valve terminal)

## Connection of valve terminals to a higher-order I-Port master

### Overview

Valve terminal with I-Port interface

Valve terminal

VTUG

- Up to 24 valve positions
- Flow rate of up to 1200 l/min

CPV

- Up to 8 valve positions
- Flow rate of up to 1200 l/min

VTUB-12

- Up to 35 valve positions
- Flow rate of up to 400 l/min


VTOC

- Up to 24 valve positions
- Flow rate of up to 10 l/min

MPA-L

- Up to 32 valve positions
- Flow rate of up to 870 l/min

CTEU bus node  
(I-Port master)



# AS-Interface® components


Bus node CTEU-AS

FESTO


| General technical data                                     |                   |        |                                                                                                                                                              |  |
|------------------------------------------------------------|-------------------|--------|--------------------------------------------------------------------------------------------------------------------------------------------------------------|--|
| Fieldbus interface                                         |                   |        | <ul style="list-style-type: none"> <li>• Plug connector M12x1, 4-pin, A-coded</li> <li>• Socket M12x1, 4-pin, A-coded</li> </ul>                             |  |
| Protocol                                                   |                   |        | AS-Interface                                                                                                                                                 |  |
| Internal cycle time                                        |                   | [ms]   | 10                                                                                                                                                           |  |
| Operating voltage                                          | Nominal value     | [V DC] | 30                                                                                                                                                           |  |
|                                                            | Permissible range | [V DC] | 20 ... 31.6                                                                                                                                                  |  |
| Intrinsic current consumption at nominal operating voltage |                   | [mA]   | Typically 50                                                                                                                                                 |  |
| Max. power supply                                          |                   | [A]    | 4                                                                                                                                                            |  |
| Max. address capacity, inputs                              |                   | [byte] | 2                                                                                                                                                            |  |
| Max. address capacity, outputs                             |                   | [byte] | 2                                                                                                                                                            |  |
| Control elements                                           |                   |        | DIL switches                                                                                                                                                 |  |
| Device-specific diagnostics                                |                   |        | <ul style="list-style-type: none"> <li>• System diagnostics</li> <li>• Undervoltage</li> <li>• Communication error</li> </ul>                                |  |
| Parameterisation                                           |                   |        | <ul style="list-style-type: none"> <li>• Watchdog enable</li> <li>• Watchdog disable</li> </ul>                                                              |  |
| LED display                                                | Bus-specific      |        | • AS-i: AS-Interface operation                                                                                                                               |  |
|                                                            | Product-specific  |        | <ul style="list-style-type: none"> <li>• PS: Operating voltage for electronics and load supply</li> <li>• X1: System status of module at I-Port 1</li> </ul> |  |
| Degree of protection to EN 60529                           |                   |        | IP65, IP67                                                                                                                                                   |  |
| Note on materials                                          |                   |        | RoHS compliant                                                                                                                                               |  |
| Information on housing materials                           |                   |        | PA reinforced                                                                                                                                                |  |
| Temperature range                                          | Environment       | [°C]   | -5 ... +50                                                                                                                                                   |  |
|                                                            | Storage           | [°C]   | -20 ... +70                                                                                                                                                  |  |
| Dimensions W x L x H                                       |                   | [mm]   | 40 x 91 x 50                                                                                                                                                 |  |
| Product weight                                             |                   | [g]    | 90                                                                                                                                                           |  |
| Corrosion resistance class CRC                             |                   |        | 2 <sup>1)</sup>                                                                                                                                              |  |
| CE marking                                                 |                   |        | To EU EMC Directive <sup>2)</sup>                                                                                                                            |  |
| Certification                                              |                   |        | c UL us – Listed (OL)                                                                                                                                        |  |

- 1) Corrosion resistance class 2 to Festo standard 940 070  
Components subject to moderate corrosion stress. External visible parts with primarily decorative surface requirements which are in direct contact with the surrounding industrial environment or media such as coolants or lubricating agents.
- 2) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: [www.festo.com/sp](http://www.festo.com/sp) → Certificates.  
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

Connection and display components



| Pin allocation                                        |     |                          |
|-------------------------------------------------------|-----|--------------------------|
|                                                       | Pin | Allocation               |
| M12 plug connector, AS-Interface, incoming connection |     |                          |
|                                                       | 1   | AS-Interface +           |
|                                                       | 2   | 24 V load voltage supply |
|                                                       | 3   | AS-Interface –           |
|                                                       | 4   | 0 V load voltage supply  |
| M12 socket, AS-interface, outgoing connection         |     |                          |
|                                                       | 1   | AS-Interface +           |
|                                                       | 2   | 24 V load voltage supply |
|                                                       | 3   | AS-Interface –           |
|                                                       | 4   | 0 V load voltage supply  |








| Type    | B1 | H1   | H2   | L1 |
|---------|----|------|------|----|
| CTEU-AS | 91 | 45,3 | 39,7 | 40 |

# AS-Interface® components

Bus node CTEU-AS – Accessories

**FESTO**

| Ordering data                                                                       |                                                                                  |                             |          |                   |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------|-----------------------------|----------|-------------------|
|                                                                                     | Designation                                                                      |                             | Part No. | Type              |
| Bus node                                                                            |                                                                                  |                             |          |                   |
|    | Bus node CTEU-AS (AS-Interface bus node)                                         |                             | 572555   | CTEU-AS           |
| Bus connection                                                                      |                                                                                  |                             |          |                   |
|    | AS-interface flat cable, yellow                                                  | 100 m                       | 18940    | KASI-1,5-Y-100    |
|                                                                                     | AS-interface flat cable, black                                                   | 100 m                       | 18941    | KASI-1,5-Z-100    |
|    | Cable cap for flat cable (pack of 50)                                            |                             | 18787    | ASI-KK-FK         |
|    | Cable sleeve (pack of 20)                                                        |                             | 165593   | ASI-KT-FK         |
|   | Socket M12, 4-pin                                                                | For AS-interface flat cable | 18789    | ASI-SD-PG-M12     |
|  | M12 socket, 5-pin                                                                | For round cable             | 18324    | FBSD-GD-9-5POL    |
| Cable distributor                                                                   |                                                                                  |                             |          |                   |
|  | AS-Interface data to socket M12, 4-pin                                           |                             | 572225   | NEFU-X22F-M12G4   |
|  | AS-Interface data and load voltage supply to socket M12, 4-pin                   |                             | 572226   | NEFU-X24F-M12G4   |
|  | AS-Interface data and load voltage supply to socket M12, 4-pin, cable length 1 m |                             | 572227   | NEFU-X24F-1-M12G4 |
| DUO plugs                                                                           |                                                                                  |                             |          |                   |
|  | Plug connector M12 for 2 connecting cables                                       | 4-pin, PG11                 | 18779    | SEA-GS-11-DUO     |
|                                                                                     |                                                                                  | 5-pin, PG11                 | 192010   | SEA-5GS-11-DUO    |



## CPV valve terminals with AS-interface – Valve configuration options

CPV valve terminals with AS-interface can be configured with a wide range of valve slices. The system supports a maximum of 8 outputs and 8 inputs per AS-interface slave.

This gives the following basic valve slice configuration options (see tables on following page). Vacant positions can be configured instead of valve slices at any position.

### General data

- With or without 24 V DC auxiliary power supply for solenoid coils (EMERGENCY-STOP circuitry) depending on bus interface
- Solutions with and without integrated inputs
- Width 10, 14 or 18 mm

### Versions

- 2, 4 or 8 valve slices
- With 4 or 8 inputs, either
  - standard mode (SPEC V2.0)
  - A/B mode (SPEC V2.1)
  - A/B mode (SPEC V3.0, profile 7.A.7)
- Optionally with floating relay outputs
- Valves with integrated separation of channels 1 and 11
- Separator plates for the creation of pressure zones
- Suitable for vacuum
- Vacant positions for subsequent extension
- Optionally with pneumatic multiple connector plate

### Application

- Cost-effective connection of 2, 4 or 8 valve slices to the AS-interface
- Comprehensive range of valve functions
- Decentralised machine and system structures, for example
  - in handling technology
  - in conveyor technology
  - in the packaging industry
  - in sorting systems
  - in upstream machine functions



#### Note

Please follow the links below for more details on the various pneumatic functions.

➔ Internet: [cpv](http://cpv)

| Types of valve terminal with AS-interface |                           |              |                |                           |                        |         |       |       |       |
|-------------------------------------------|---------------------------|--------------|----------------|---------------------------|------------------------|---------|-------|-------|-------|
| Code                                      | Type                      | Valve slices | Solenoid coils | Inputs<br>(M8 connection) | Auxiliary power supply |         | Size  |       |       |
|                                           |                           |              |                |                           | With                   | Without | CPV10 | CPV14 | CPV18 |
| AZ                                        | CPV1x-GE-ASI-2-Z          | 2            | 4              | –                         | ■                      | –       | ■     | ■     | ■     |
| AZ                                        | CPV18-GE-ASI-4-Z          | 4            | 4              | –                         | ■                      | –       | –     | –     | ■     |
| AE/AO                                     | CPV1x-GE-ASI-4E4A (-Z)    | 4            | 4              | 4                         | ■                      | ■       | ■     | ■     | –     |
| AE                                        | CPV1x-GE-ASI-8E8A-Z       | 8            | 8              | 8                         | ■                      | –       | ■     | ■     | –     |
| BE                                        | CPV1x-GE-ASI-4E3A (-Z)    | 4            | 3              | 4                         | ■                      | –       | ■     | ■     | –     |
| BE                                        | CPV1x-GE-ASI-8E6A-Z       | 8            | 6              | 8                         | ■                      | –       | ■     | ■     | –     |
| CE                                        | CPV1x-GE-ASI-4E4A-Z-M8-CE | 4            | 4              | 4                         | ■                      | –       | ■     | ■     | –     |
| CE                                        | CPV1x-GE-ASI-8E8A-Z-M8-CE | 8            | 8              | 8                         | ■                      | –       | ■     | ■     | –     |

1) The load voltage (auxiliary power supply via the black cable) can be connected/disconnected separately.

| Permissible combinations in valve position allocation |         |                 |     |                 |           |                 |     |                 |
|-------------------------------------------------------|---------|-----------------|-----|-----------------|-----------|-----------------|-----|-----------------|
| Type                                                  | Slave n |                 |     |                 | Slave n+1 |                 |     |                 |
|                                                       | 0       | 1               | 2   | 3               | 4         | 5               | 6   | 7               |
| CPV1x-GE-ASI-2-Z                                      | M       | M               |     |                 |           |                 |     |                 |
|                                                       | J       | M               |     |                 |           |                 |     |                 |
|                                                       | M       | J               |     |                 |           |                 |     |                 |
|                                                       | J       | J               |     |                 |           |                 |     |                 |
| CPV18-GE-ASI-4-Z                                      | M       | M               | M   | M               |           |                 |     |                 |
| CPV1x-GE-ASI-4E4A (-Z)                                | M       | M               | M   | M               |           |                 |     |                 |
| CPV10-GE-ASI-4A (-Z)                                  | J       | Vacant position | M   | M               |           |                 |     |                 |
| CPV14-GE-ASI-4A (-Z)                                  | M       | M               | J   | Vacant position |           |                 |     |                 |
|                                                       | J       | Vacant position | J   | Vacant position |           |                 |     |                 |
| CPV1x-GE-ASI-4E3A -Z <sup>1)</sup>                    | M       | M               | M   | Vacant position |           |                 |     |                 |
|                                                       | J       | Vacant position | M   | Vacant position |           |                 |     |                 |
| CPV1x-GE-ASI-8E8A-Z <sup>1)</sup>                     | M       | M               | M   | M               | M         | M               | M   | M               |
| CPV1x-GE-ASI-8E8A-Z-CE <sup>1)</sup>                  | J       | Vacant position | M   | M               | M         | M               | M   | M               |
|                                                       | M       | M               | J   | Vacant position | M         | M               | M   | M               |
|                                                       | J       | Vacant position | J   | Vacant position | M         | M               | M   | M               |
|                                                       | ...     | ...             | ... | ...             | ...       | ...             | ... | ...             |
|                                                       | M       | M               | M   | M               | M         | M               | M   | M               |
|                                                       | M       | M               | M   | M               | J         | Vacant position | M   | M               |
|                                                       | M       | M               | M   | M               | M         | M               | J   | Vacant position |
|                                                       | M       | M               | M   | M               | J         | Vacant position | J   | Vacant position |
| CPV1x-GE-ASI-8E6A-Z <sup>1)</sup>                     | M       | M               | M   | Vacant position | M         | M               | M   | Vacant position |
|                                                       | M       | M               | M   | Vacant position | J         | Vacant position | M   | Vacant position |
|                                                       | J       | Vacant position | M   | Vacant position | M         | M               | M   | Vacant position |
|                                                       | J       | Vacant position | M   | Vacant position | J         | Vacant position | M   | Vacant position |

- 1) - Valve slices with 2 outputs must be configured at positions 0, 2, 4, 6 (or positions 0, 4 with A/B mode).  
 - Valve slices with 2 outputs always have a vacant position.  
 - Slaves n and n+1 can be configured independently of one another. This gives a total of 16 different configuration options.
- M Valve slice with single solenoid valve or a different valve slice with an output.  
 J Valve slice with double solenoid valve or a different valve slice with two outputs.

## AS-interface® components

CPV valve terminals with integrated inputs, to SPEC V2.0

FESTO



### CPV valve terminals with integrated inputs, to Specification V2.0

#### General data

- Cubic design for exceptional performance and low weight
- Highly flexible thanks to various pneumatic functions (valve variants), different pressure ranges, vacuum switches and the option of integrated vacuum generation
- Floating relay outputs (optional)
- Connection for auxiliary power supply for EMERGENCY-STOP conditions
- Protection class IP65

#### LED displays for:

- Status display for inputs
- Switching status of valves
- PWR-LED (power)
- FAULT-LED (fault)

#### Versions

- Width 10 and 14 mm
- 4 or 8 inputs
- 4 or 8 valve positions
- Up to four pressure zones
- Suitable for vacuum
- Vacuum generation

- Various valve functions on one valve terminal, for example
  - 2x 3/2-way valve
  - 5/2-way valve, single solenoid
  - 5/2-way valve, double solenoid
  - 5/3-way valve
  - 2x 2/2-way valve
  - Valves with integrated separation of channels 1 and 11
  - Separator plate
  - Vacant position
- Additional function (screwed onto valve slice)
  - One-way flow control valve
- Various mounting options

#### Application

- Flexible and cost-effective connection of 4 or 8 valve slices and up to 8 sensors to the M8 inputs to Spec. V2.0, 31 slaves, bus cycle max. 5 ms. Executable on all masters from Spec. V2.0 or higher.



Note

Please follow the links below for more details on the various pneumatic functions.

➔ Internet: cpv

# AS-interface® components

CPV valve terminals with integrated inputs, to SPEC V2.0


FESTO

| Technical data             |                                                        |                                                                                       |                            |                              |
|----------------------------|--------------------------------------------------------|---------------------------------------------------------------------------------------|----------------------------|------------------------------|
| Type                       |                                                        | CPV-...-GE-ASI-4E4A-Z-M8                                                              | CPV-...-GE-ASI-4E4A-M8     | CPV-...-GE-ASI-8E8A-Z-M8     |
| Part No.                   |                                                        | Order via order code/valve terminal configurator                                      |                            |                              |
| Code                       |                                                        | AE                                                                                    | AO                         | AE                           |
| Valves                     | Number of valve slices/coils                           | 4                                                                                     | 4                          | 8                            |
|                            | Valve width [mm]                                       | 10/14                                                                                 |                            |                              |
|                            | Setting of the valve configuration                     | Integrated DIL switch                                                                 |                            |                              |
|                            | External power supply<br>24 V DC                       | Yes                                                                                   | No                         | Yes                          |
|                            | Digital inputs                                         | 4                                                                                     | 4                          | 8                            |
|                            | Connection technology                                  | M8, 3-pin                                                                             |                            |                              |
|                            | Sensor supply via AS-interface                         | Short circuit and overload proof                                                      |                            |                              |
|                            | Sensor connection                                      | 2-wire and 3-wire sensors                                                             |                            |                              |
|                            | Type                                                   | IEC 1131-2, type 2                                                                    |                            |                              |
|                            | Input circuitry                                        | PNP (positive switching)                                                              |                            |                              |
| AS-interface<br>connection | Connection technology                                  | AS-interface flat cable plug (included in scope of delivery)                          |                            |                              |
|                            | Voltage range [V DC]                                   | 26.5 ... 31.6, reverse polarity protected                                             |                            |                              |
|                            | Residual ripple [mVss]                                 | 20                                                                                    |                            |                              |
|                            | Current consumption [mA]<br>of inputs                  |                                                                                       | CPV10/14                   |                              |
|                            | • In 0 status                                          | 7                                                                                     | 61/95                      | 40                           |
|                            | • In 1 status (no current consumption<br>by sensors)   | 35                                                                                    | 89/123                     | 96                           |
|                            | • In 1 status (max. current<br>consumption by sensors) | 240                                                                                   | 191/225                    | 278                          |
|                            | • Max. per input                                       | 200                                                                                   | 200                        | 200                          |
| Load voltage<br>connection | Connection technology                                  | AS-interface flat cable plug (version turned through 180° must be ordered separately) |                            |                              |
|                            | Nominal voltage [V DC]                                 | 24 ±10%                                                                               |                            |                              |
|                            | Residual ripple [Vss]                                  | 4                                                                                     |                            |                              |
|                            | Current consumption of<br>valves                       | CPV10/14                                                                              | No load voltage connection | CPV10/14                     |
|                            | • when switching on [mA]                               | 108/176                                                                               |                            | 200/310                      |
|                            | • following a current<br>reduction [mA]                | 42/72                                                                                 |                            | 70/100                       |
|                            |                                                        |                                                                                       |                            |                              |
|                            |                                                        |                                                                                       |                            |                              |
| LED displays               | ASI-LED                                                | Power/green                                                                           |                            |                              |
|                            | AUX-PWR-LED                                            | Auxiliary power supply/green                                                          | None                       | Auxiliary power supply/green |
|                            | FAULT-LED                                              | Fault LED/red                                                                         |                            |                              |
|                            | Inputs                                                 | Green                                                                                 |                            |                              |
|                            | Valves                                                 | Yellow                                                                                |                            |                              |
| General<br>data            | Protection class (to EN 60529)                         | IP65 (fully assembled)                                                                |                            |                              |
|                            | Electromagnetic compatibility                          |                                                                                       |                            |                              |
|                            | • Interference emission                                | Tested to EN 55011, limit value class B                                               |                            |                              |
|                            | • Interference immunity                                | Tested to DIN EN 61000-4-2, DIN EN 61000-4-4 and EN V 50140                           |                            |                              |
|                            | CE mark                                                | Yes, in accordance with EU Directive 89/336/EEC                                       |                            |                              |
|                            | Temperature range [°C]                                 | Operation: -5 ... +50; storage/transport: -20 ... +70                                 |                            |                              |
|                            | Materials                                              | Housing: aluminium; cover: polyamide; seals: nitrile rubber; polychloroprene rubber   |                            |                              |
|                            | Dimensions                                             | ➔ 32                                                                                  |                            |                              |
|                            | Weight                                                 | ➔ 32                                                                                  |                            |                              |
| AS-interface<br>data       | Pneumatic data                                         | ➔ Internet: cpv                                                                       |                            |                              |
|                            | ID code                                                | F <sub>H</sub> (ID = F <sub>H</sub> ; ID1 = F <sub>H</sub> ; ID2 = F <sub>H</sub> )   |                            |                              |
|                            | IO code                                                | 7 <sub>H</sub>                                                                        |                            |                              |
|                            | Profile                                                | S-7.F                                                                                 |                            |                              |

## AS-interface® components

CPV valve terminals with integrated inputs, for A/B mode to SPEC V2.1

FESTO



### CPV valve terminals with integrated inputs, for A/B mode to Specification V2.1<sup>1)</sup>

#### General data

- A/B mode increases the performance of each master
  - 100% more inputs (248 instead of 124)
  - 50% more outputs (186 instead of 124)
- Cubic design for exceptional performance and low weight
- Highly flexible thanks to various pneumatic functions (valve variants), different pressure ranges, vacuum switches and the option of integrated vacuum generation
- Floating relay outputs, optional

- Connection for auxiliary power supply for EMERGENCY-STOP conditions
  - Protection class IP65
- LED displays for:
- Status display for inputs
  - Switching status displays for valves
  - PWR-LED (power)
  - FAULT-LED (fault)<sup>2)</sup>

#### Versions

- Width 10 and 14 mm
- 4 or 8 inputs
- 3 or 6 valve positions

- Up to four pressure zones
- Suitable for vacuum
- Vacuum generation
- Various valve functions on one valve terminal, for example
  - 2x 3/2-way valve
  - 5/2-way valve, single solenoid
  - 5/2-way valve, double solenoid
  - 5/3-way valve
  - 2x 2/2-way valve
  - Valves with integrated separation of channels 1 and 11
  - Separator plate
  - Vacant position

- Additional function (screwed onto valve slice)
  - One-way flow control valve
- Various mounting options

#### Application

- AS-i networks with A/B mode to SPEC V2.1 and SPEC V3.0, 62 slaves, bus cycle 10 ms
- Flexible and cost-effective connection of 3 or 6 valve slices and up to 8 sensors to the M8 inputs



Note

Please follow the links below for more details on the various pneumatic functions.

→ Internet: cpv

1) Slave compatible with SPEC V3.0

2) Peripherals faults to SPEC V2.1 not yet implemented

# AS-interface® components

FESTO


CPV valve terminals with integrated inputs, for A/B mode to SPEC V2.1

| Technical data          |                                                     |                                                                                       |                          |
|-------------------------|-----------------------------------------------------|---------------------------------------------------------------------------------------|--------------------------|
| Type                    |                                                     | CPV-...-GE-ASI-4E3A-Z-M8                                                              | CPV-...-GE-ASI-8E6A-Z-M8 |
| Part No.                |                                                     | Order via order code/valve terminal configurator                                      |                          |
| Code                    |                                                     | BE                                                                                    | BE                       |
| Valves                  | Number of valve slices/coils                        | 3                                                                                     | 6                        |
|                         | Valve width [mm]                                    | 10/14                                                                                 |                          |
|                         | Setting of the valve configuration                  | Integrated DIL switch                                                                 |                          |
|                         | External power supply 24 V DC                       | Yes                                                                                   |                          |
|                         | Digital inputs                                      | 4                                                                                     | 8                        |
|                         | Connection technology                               | M8, 3-pin                                                                             |                          |
|                         | Sensor supply via AS-interface                      | Short circuit and overload proof                                                      |                          |
|                         | Sensor connection                                   | 2-wire and 3-wire sensors                                                             |                          |
|                         | Type                                                | IEC 11 31-2, type 2                                                                   |                          |
|                         | Input circuitry                                     | PNP (positive switching)                                                              |                          |
| AS-interface connection | Connection technology                               | AS-interface flat cable plug (included in scope of delivery)                          |                          |
|                         | Voltage range [V DC]                                | 26.5 ... 31.6, reverse polarity protected                                             |                          |
|                         | Residual ripple [mVss]                              | 20                                                                                    |                          |
|                         | Current consumption of inputs [mA]                  |                                                                                       |                          |
|                         | • In 0 status                                       | 7                                                                                     | 40                       |
|                         | • In 1 status (no current consumption by sensors)   | 35                                                                                    | 96                       |
|                         | • In 1 status (max. current consumption by sensors) | 137                                                                                   | 278                      |
| Load voltage connection | • Max. per input                                    | 200                                                                                   | 200                      |
|                         | Connection technology                               | AS-interface flat cable plug (version turned through 180° must be ordered separately) |                          |
|                         | Nominal voltage [V DC]                              | 24 ±10%                                                                               |                          |
|                         | Residual ripple [Vss]                               | 4                                                                                     |                          |
|                         | Current consumption of valves                       | CPV10/14                                                                              | CPV10/14                 |
|                         | • when switching on [mA]                            | 81/132                                                                                | 150/233                  |
|                         | • following a current reduction [mA]                | 32/54                                                                                 | 53/75                    |
| LED displays            | ASI-LED                                             | Power/green                                                                           |                          |
|                         | AUX-PWR-LED                                         | Auxiliary power supply/green                                                          |                          |
|                         | FAULT-LED                                           | Fault LED/red                                                                         |                          |
|                         | Inputs                                              | Green                                                                                 |                          |
|                         | Valves                                              | Yellow                                                                                |                          |
| General data            | Protection class (to EN 60529)                      | IP65 (fully assembled)                                                                |                          |
|                         | Electromagnetic compatibility                       |                                                                                       |                          |
|                         | • Interference emission                             | Tested to EN 55011, limit value class B                                               |                          |
|                         | • Interference immunity                             | Tested to DIN EN 61000-4-2, DIN EN 61000-4-4 and EN V 50140                           |                          |
|                         | CE mark                                             | Yes, in accordance with EU Directive 89/336/EEC                                       |                          |
|                         | Temperature range [°C]                              | Operation: -5 ... +50; storage/transport: -20 ... +70                                 |                          |
|                         | Materials                                           | Housing: aluminium; cover: polyamide; seals: nitrile rubber, polychloroprene rubber   |                          |
|                         | Dimensions                                          | ➔ 32                                                                                  |                          |
|                         | Weight                                              | ➔ 32                                                                                  |                          |
| AS-interface data       | Pneumatic data                                      | ➔ Internet: cpv                                                                       |                          |
|                         | ID code                                             | ID = A <sub>H</sub> ; ID1 = 7 <sub>H</sub> ; ID2 = E <sub>H</sub>                     |                          |
|                         | IO code                                             | 7 <sub>H</sub>                                                                        |                          |
|                         | Profile                                             | S-7.A.E                                                                               |                          |

# AS-interface® components

CPV valve terminals with integrated inputs, for A/B mode to SPEC V3.0

FESTO



## CPV valve terminals with integrated inputs, for A/B mode to specification V3.0, profile 7.A.7

### General data

- A/B mode increases the performance of each master
  - 100% more inputs (248 instead of 124)
  - 100% more outputs (248 instead of 124)
- Cubic design for exceptional performance and low weight
- Highly flexible thanks to various pneumatic functions (valve variants), different pressure ranges, vacuum switches and the option of integrated vacuum generation
- Floating relay outputs, optional

- Connection for auxiliary power supply for EMERGENCY-STOP conditions
  - Protection class IP65
- LED displays for:
- Status display for inputs
  - Switching status displays for valves
  - PWR-LED (power)
  - FAULT-LED (fault)

### Versions

- Width 10 and 14 mm
- 4 or 8 inputs
- 4 or 8 valve positions

- Up to four pressure zones
- Suitable for vacuum
- Vacuum generation
- Various valve functions on one valve terminal, for example
  - 2x 3/2-way valve
  - 5/2-way valve, single solenoid
  - 5/2-way valve, double solenoid
  - 5/3-way valve
  - 2x 2/2-way valve
  - Valves with integrated separation of channels 1 and 11
  - Separator plate
  - Vacant position

- Additional function (screwed onto valve slice)
  - One-way flow control valve
- Various mounting options

### Application

- AS-i networks with A/B mode to SPEC V3.0, profile 7.A.7, 62 slaves, bus cycle 20 ms
- Flexible and cost-effective connection of 4 or 8 valve slices and up to 8 sensors to the M8 inputs



### Note

Slaves to Specification V3.0 require an ASI master to Specification V3.0; these detect the new slave profiles automatically.

Please follow the links below for more details on the various pneumatic functions.

➔ Internet: cpv

# AS-interface® components

FESTO

CPV valve terminals with integrated inputs, for A/B mode to SPEC V3.0

| Technical data          |                                                   |                                                                                              |                             |
|-------------------------|---------------------------------------------------|----------------------------------------------------------------------------------------------|-----------------------------|
| Type                    |                                                   | CPV-...-GE-ASI-4E4A-Z M8-CE                                                                  | CPV-...-GE-ASI-8E8A-Z M8-CE |
| Part No.                | Order via order code/valve terminal configurator  |                                                                                              |                             |
| Code                    | CE                                                |                                                                                              |                             |
| Valves                  | Number of valve slices/coils                      | 4                                                                                            | 8                           |
|                         | Valve width [mm]                                  | 10/14                                                                                        |                             |
|                         | Setting of the valve configuration                | Integrated DIL switch                                                                        |                             |
|                         | External power supply [V DC]                      | 24                                                                                           |                             |
|                         | Digital inputs                                    | 4                                                                                            | 8                           |
|                         | Connection technology                             | M8, 3-pin                                                                                    |                             |
|                         | Device-specific diagnostics                       | Short circuit/overload of inputs                                                             |                             |
|                         | Sensor connection                                 | 2-wire and 3-wire sensors                                                                    |                             |
|                         | Input characteristic                              | IEC 1131-2, type 2                                                                           |                             |
|                         | Switching logic at inputs                         | PNP (positive switching)                                                                     |                             |
| AS-interface connection | Connection technology                             | AS-interface flat cable plug (included in scope of delivery)                                 |                             |
|                         | Number of slaves per device                       | 1                                                                                            | 2                           |
|                         | Voltage range [V DC]                              | 26.5 ... 31.6, reverse polarity protected                                                    |                             |
|                         | Residual ripple [mVss]                            | 20                                                                                           |                             |
|                         | Debounce time at inputs (at 24 V) [ms]            | Typically 3                                                                                  |                             |
|                         | Set using AS-interface addressing device          | 1A ... 31A (0)<br>1B ... 31B                                                                 |                             |
|                         | Switching level [V]                               |                                                                                              |                             |
|                         | Signal 0                                          | ≤ 5                                                                                          |                             |
|                         | Signal 1                                          | ≥ 11                                                                                         |                             |
|                         | Current consumption of inputs [mA]                |                                                                                              |                             |
|                         | • In 0 status                                     | 20                                                                                           | 40                          |
|                         | • In 1 status (no current consumption by sensors) | Max. 48                                                                                      | Max. 96                     |
|                         | • Max. per input                                  | 200                                                                                          | 200                         |
| Load voltage connection | Connection technology                             | AS-interface flat cable plug (version turned through 180° must be ordered separately)        |                             |
|                         | Nominal voltage [V DC]                            | 24 ±10%                                                                                      |                             |
|                         | Residual ripple [Vss]                             | 4                                                                                            |                             |
|                         | Current consumption of valves (type-dependent)    | CPV10/14                                                                                     | CPV10/14                    |
|                         | • when switching on [mA]                          | Max. 115/175                                                                                 | Max. 240/460                |
|                         | • following a current reduction [mA]              | Max. 55/75                                                                                   | Max. 95/120                 |
| LED displays            | ASI-LED                                           | Power/green                                                                                  |                             |
|                         | AUX-PWR-LED                                       | Auxiliary power supply/green                                                                 |                             |
|                         | FAULT-LED                                         | Fault LED/red                                                                                |                             |
|                         | Inputs                                            | Green                                                                                        |                             |
|                         | Valves                                            | Yellow                                                                                       |                             |
| General data            | Protection class (to EN 60529)                    | IP65 (fully assembled)                                                                       |                             |
|                         | Relative air humidity [%]                         | 0 ... 95 (non-condensing)                                                                    |                             |
|                         | CE mark                                           | To EU EMC Directive                                                                          |                             |
|                         | Temperature range [°C]                            | Operation: -5 ... +50; storage/transport: -20 ... +70                                        |                             |
|                         | Materials                                         | Housing: aluminium die-cast; cover: polyamide; seals: nitrile rubber, polychloroprene rubber |                             |
|                         | Dimensions                                        | ➔ 32                                                                                         |                             |
|                         | Weight                                            | ➔ 32                                                                                         |                             |
|                         | Pneumatic data                                    | ➔ Internet: cpv                                                                              |                             |
| AS-interface data       | ID code                                           | ID = A <sub>H</sub> ; ID1 = 7 <sub>H</sub> ; ID2 = 7 <sub>H</sub>                            |                             |
|                         | IO code                                           | 7 <sub>H</sub>                                                                               |                             |
|                         | Profile                                           | S-7.A.7                                                                                      |                             |

# AS-interface® components

CPV valve terminals without inputs, to SPEC V2.1

FESTO



## CPV valve terminals without inputs, to Specification V2.1<sup>1)</sup>

### General data

- Cubic design for exceptional performance and low weight
- Highly flexible thanks to various pneumatic functions (valve variants), different pressure ranges, vacuum switches and the option of integrated vacuum generation
- Floating relay outputs, optional
- Connection for auxiliary power supply for EMERGENCY-STOP conditions
- Protection class IP65

### LED displays for:

- Switching status displays for valves
- PWR-LED (power)
- FAULT-LED (fault)<sup>2)</sup>
- Valve diagnostics: short circuit or wire break at valve solenoid coil, valve does not respond (no movement of the plunger)

### Versions

- Width 10, 14 and 18 mm
- 2 or 4 valve positions
- Up to two pressure zones
- Suitable for vacuum
- Vacuum generation

- Valve terminal with 4 valve positions:
  - With or without 24 V DC auxiliary power supply for solenoid coils (EMERGENCY-STOP circuitry)
  - The auxiliary power supply is always integrated and can be subsequently switched off using the DIL switch
- Various valve functions on one valve terminal, for example
  - 2x 3/2-way valve
  - 5/2-way valve, single solenoid
  - 5/2-way valve, double solenoid
  - 5/3-way valve
- 2x 2/2-way valve
- Valves with integrated separation of channels 1 and 11
- Separator plate
- Vacant position
- Additional function (screwed onto valve slice)
  - One-way flow control valve
- Extensive mounting options

### Application

- Flexible and cost-effective connection of 2 or 4 valve slices, 31 slaves, bus cycle max. 5 ms



Note

Please follow the links below for more details on the various pneumatic functions.

➔ Internet: cpv

1) Slave compatible with SPEC V3.0

2) Valve terminal with 4 valve positions: peripherals faults to SPEC V2.1 implemented  
Valve terminal with 2 valve positions: peripherals faults not implemented

# AS-interface® components

CPV valve terminals without inputs, to SPEC V2.1

FESTO

| Technical data                |                                    |                                                  |                                                                                                                                                         |                                            |
|-------------------------------|------------------------------------|--------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------|
| Type                          |                                    | CPV-...-GE-ASI-2-Z                               |                                                                                                                                                         | CPV-...-GE-ASI-4-Z <sup>1)</sup>           |
| Part No.                      |                                    | Order via order code/valve terminal configurator |                                                                                                                                                         |                                            |
| Code                          |                                    | AZ                                               |                                                                                                                                                         | AS/AZ                                      |
| Valves                        | Number of valve slices/coils       |                                                  | 2/4                                                                                                                                                     |                                            |
|                               | Valve width                        | 10 mm                                            | ■                                                                                                                                                       | ■                                          |
|                               |                                    | 14 mm                                            | ■                                                                                                                                                       | ■                                          |
|                               |                                    | 18 mm                                            | ■                                                                                                                                                       | ■                                          |
|                               | Setting of the valve configuration |                                                  | None (permanently assigned)                                                                                                                             |                                            |
|                               | External power supply              |                                                  | Yes                                                                                                                                                     |                                            |
|                               |                                    | 24 V DC                                          |                                                                                                                                                         | Yes <sup>2)</sup><br>Set using DIL switch  |
| AS-interface connection       | Connection technology              |                                                  | AS-interface flat cable plug (must be ordered separately)                                                                                               |                                            |
|                               | Voltage range                      | [V DC]                                           | 26.5 ... 31.6, reverse polarity protected                                                                                                               |                                            |
|                               | Residual ripple                    | [mVss]                                           | 20                                                                                                                                                      |                                            |
|                               | Current consumption of all valves  |                                                  | CPV10/14/18                                                                                                                                             |                                            |
|                               | • without current reduction        |                                                  | [mA] 25/25/25                                                                                                                                           |                                            |
|                               | • with current reduction           |                                                  | [mA] 25/25/25                                                                                                                                           |                                            |
| Load voltage connection       | Connection technology              |                                                  | AS-interface flat cable plug (must be ordered separately)                                                                                               |                                            |
|                               |                                    |                                                  | Blanking plug for sealing the unused connection enclosed                                                                                                |                                            |
|                               | Nominal voltage                    | [V DC]                                           | 24 ±10%                                                                                                                                                 |                                            |
|                               | Residual ripple                    | [Vss]                                            | 4                                                                                                                                                       |                                            |
|                               | Max. starting current              |                                                  | CPV10/14/18                                                                                                                                             |                                            |
|                               | • before current reduction         |                                                  | [mA] 108/176/320                                                                                                                                        |                                            |
| LED displays                  | PWR-LED                            |                                                  | Power/green                                                                                                                                             |                                            |
|                               | FAULT-LED                          |                                                  | Fault LED/red                                                                                                                                           |                                            |
|                               |                                    |                                                  | Peripherals fault LED/red<br>Valve diagnostics: short circuit or wire break at valve solenoid coil, valve does not respond (no movement of the plunger) |                                            |
|                               | Valves                             |                                                  | Yellow                                                                                                                                                  |                                            |
| General data                  | Protection class (to EN 60 529)    |                                                  | IP65 (fully assembled)                                                                                                                                  |                                            |
|                               | Electromagnetic compatibility      |                                                  |                                                                                                                                                         |                                            |
|                               | • Interference emission            |                                                  | Tested to EN 55011, limit value class B                                                                                                                 |                                            |
|                               | • Interference immunity            |                                                  | Tested to DIN EN 61000-4-2, DIN EN 61000-4-4 and EN V 50140                                                                                             |                                            |
|                               | CE mark                            |                                                  | Yes, in accordance with EU Directive 89/336/EEC                                                                                                         |                                            |
|                               | Temperature range                  | [°C]                                             | Operation: -5 ... +50; storage/transport: -20 ... +70                                                                                                   |                                            |
|                               | Materials                          |                                                  | Housing: aluminium die-cast; cover: polyamide; seals: nitrile rubber, polychloroprene rubber                                                            |                                            |
|                               | Dimensions                         |                                                  | ➔ 32                                                                                                                                                    |                                            |
| AS-interface data             | Weight                             |                                                  | ➔ 32                                                                                                                                                    |                                            |
|                               | Pneumatic data                     |                                                  | ➔ Internet: cpv                                                                                                                                         |                                            |
|                               | ID code                            |                                                  | F <sub>H</sub>                                                                                                                                          |                                            |
|                               | IO code                            |                                                  | 8 <sub>H</sub>                                                                                                                                          |                                            |
|                               | ID2 code                           |                                                  | F <sub>H</sub>                                                                                                                                          | E <sub>H</sub> (F <sub>H</sub> with CPV18) |
|                               | Profile                            |                                                  | S-8.F                                                                                                                                                   |                                            |
|                               | Parameter P3                       |                                                  | 1 = enable                                                                                                                                              |                                            |
| CPV valve diagnostic function |                                    |                                                  | 2 = disable                                                                                                                                             |                                            |
|                               | Default                            |                                                  | 1 for CPV with valve diagnostics                                                                                                                        |                                            |

1) New as of hardware status 0105: single or double solenoid valves can be configured by means of a DIL switch.

2) With or without 24 V DC auxiliary power supply for solenoid coils (EMERGENCY-STOP circuitry). The auxiliary power supply is always integrated and can be switched on/off using the DIL switch.

3) None (permanently assigned)


# AS-interface® components

CPV valve terminals – Connections/displays

FESTO


## Overview of connections/displays – CPV with AS-interface

CPV-...-GE-ASI-2-Z / ASI-4-(Z)




- 1 AS-interface bus connection
- 2 PWR LED (power, green)  
Fault LED (fault, red)
- 3 Auxiliary power supply for valves (optional)
- 4 Inscription areas
- 5 LED display for valves

CPV-...-GE-ASI-4E4A-(Z) / 4E/3A-...- / 4E/4A-...-CE



- 1 AS-interface bus connection
- 2 PWR LED (power, green)  
Fault LED (fault, red)
- 3 Auxiliary power supply for valves (optional)
- 4 LED display for inputs (green)
- 5 Sensor connections
- 6 Inscription areas
- 7 LED display for valves (yellow)

CPV-...-GE-ASI-8E8A-Z / 8E/6A / 8E/8A-...-CE



- 1 AS-interface bus connection
- 2 PWR LED (power, green)  
Fault LED (fault, red)
- 3 Auxiliary power supply for valves (optional)
- 4 LED display for inputs (green)
- 5 Address selector button with LED
- 6 Sensor connections
- 7 Inscription areas
- 8 LED display for valves (yellow)

| Pin allocation |     |            |
|----------------|-----|------------|
| Inputs CPV     | Pin | Allocation |
|                | 1   | +24 V      |
|                | 3   | 0 V        |
|                | 4   | Input      |

# AS-interface® components

CPV valve terminals – Weights/dimensions


FESTO

| Weights [g] – Valve terminal CPV with AS-interface       |       |       |       |
|----------------------------------------------------------|-------|-------|-------|
| Type                                                     | CPV10 | CPV14 | CPV18 |
| Electrical connection plate with AS-interface connection |       |       |       |
| • with 2 valve positions                                 | 85    | 130   | 275   |
| • with 4(3) valve positions                              | 110   | 175   | 355   |
| • with 8(6) valve positions                              | 200   | 300   |       |
| End plate, 2 pieces                                      | 160   | 280   | 740   |
| Pneumatic multiple connector plate                       |       |       |       |
| • on CP valve terminal with 2 valve positions            | 120   | 270   | 520   |
| • on CP valve terminal with 4 valve positions            | 165   | 390   | 750   |
| • on CP valve terminal with 6 valve positions            | 225   | 510   | 870   |
| • on CP valve terminal with 8 valve positions            | 270   | 630   | 1300  |
| Flat plate silencer                                      | 147   | 234   | –     |
| Relay plate                                              | 35    | 55    | –     |
| Blanking plate                                           | 25    | 45    | 90    |
| Separator plate                                          | 25    | 45    | 90    |
| Valve plate/vacuum generator                             | 65    | 110   | 260   |
| Functional module: One-way flow control valves           | 25    | 54    | 125   |

## Dimensions – CPV with AS-interface


Download CAD data → [www.festo.com](http://www.festo.com)

Without integrated inputs




|       |        | L1  | L2    | L3    | L4  | L5   | L6 | L7  | L12  | L14  | L15  | L16  | L17  |
|-------|--------|-----|-------|-------|-----|------|----|-----|------|------|------|------|------|
| CPV10 | 2-fold | 50  | 41.8  | 62    | 71  | 52.8 | 15 | 9.5 | –    | 10.9 | 38.1 | 2.5  | 35.5 |
|       | 4-fold | 70  | 61.8  | 62    | 71  | 52.8 | 15 | 9.5 | 23.5 | 10.9 | 38.1 | 2.5  | 35.5 |
| CPV14 | 2-fold | 68  | 58    | 78    | 89  | 58.8 | 20 | 9.5 | –    | 14   | 52   | 5    | 35.5 |
|       | 4-fold | 96  | 86    | 78    | 89  | 58.8 | 20 | 9.5 | 23.5 | 14   | 52   | 5    | 35.5 |
| CPV18 | 2-fold | 96  | 85.5  | 106.5 | 118 | 73   | 20 | 9.5 | –    | 27.4 | 68.2 | 10.4 | 40   |
|       | 4-fold | 132 | 121.5 | 106.5 | 118 | 73   | 20 | 9.5 | 28   | 27.4 | 68.2 | 10.4 | 40   |

## CPV10/14 with integrated inputs



## CPV10 with integrated inputs




|       |        | L1  | L2    | L3 | L4 | L5   | L6 | L7  | L18  | L19  | L20  | L21 |
|-------|--------|-----|-------|----|----|------|----|-----|------|------|------|-----|
| CPV10 | 4-fold | 70  | 61.8  | 62 | 71 | 52.8 | 15 | 9.5 | 10.9 | 38.1 | 35   | 3   |
|       | 8-fold | 110 | 101.8 |    |    |      |    |     | 10.4 | 38.6 | 31.9 |     |
| CPV14 | 4-fold | 96  | 86    | 78 | 89 | 58.8 | 20 | 9.5 | 18.8 | 46.8 | 43.3 | 5   |

## Dimensions – CPV with AS-interface

Download CAD data → [www.festo.com](http://www.festo.com)

CPV14 with integrated inputs








- 1 Slots for inscription labels
- 2 Pneumatic multiple connector plate
- 3 Inscription label holder  
(CPV14-VI-BZ-T-... or  
CPV14-VI-ST-T-...)

|       |        | L1  | L2  | L3 | L4 | L5   | L6 | L7  | L18  | L19  | L20  | L21 |
|-------|--------|-----|-----|----|----|------|----|-----|------|------|------|-----|
| CPV14 | 8-fold | 152 | 142 | 78 | 89 | 58.8 | 20 | 9.5 | 18.8 | 46.8 | 46.3 | 5   |

# AS-interface® components

CPV valve terminals – Accessories





**FESTO**


| Ordering data                                                                       |                                                          |                       |          |                      |
|-------------------------------------------------------------------------------------|----------------------------------------------------------|-----------------------|----------|----------------------|
|                                                                                     | Description                                              |                       | Part No. | Type                 |
| Bus connection                                                                      |                                                          |                       |          |                      |
|    | AS-interface flat cable, yellow                          | 100 m                 | 18940    | KASI-1,5-Y-100       |
|                                                                                     | AS-interface flat cable, black                           | 100 m                 | 18941    | KASI-1,5-Z-100       |
|    | Flat cable socket                                        |                       | 18785    | ASI-SD-FK            |
|    | Flat cable socket                                        | Turned through 180°   | 196089   | ASI-SD-FK180         |
|    | Flat cable blanking plug                                 |                       | 196090   | ASI-SD-FK-BL         |
|    | AS-interface flat cable distributor                      | Parallel cable        | 18786    | ASI-KVT-FK           |
|   | AS-interface flat cable distributor                      | Symmetrical cable     | 18797    | ASI-KVT-FK-S         |
|  | Cable cap for flat cable (scope of delivery 50 pieces)   |                       | 18787    | ASI-KK-FK            |
|  | Cable sleeve (scope of delivery 20 pieces)               |                       | 165593   | ASI-KT-FK            |
|                                                                                     |                                                          |                       |          |                      |
| Sensor plugs                                                                        |                                                          |                       |          |                      |
|  | Straight sensor plug                                     | M8, screw-in, 3-pin   | 192009   | SEA-3GS-M8-S         |
|  | Straight sensor plug                                     | M8, solderable, 3-pin | 18696    | SEA-GS-M8            |
|  | Cover cap (scope of delivery 10 pieces)                  | M8                    | 177672   | ISK-M8               |
|                                                                                     |                                                          |                       |          |                      |
| Connecting cable                                                                    |                                                          |                       |          |                      |
|  | Modular system for connecting cables<br>➔ Internet: nebu |                       | –        | NEBU-...             |
|                                                                                     | Straight plug M8, 3-pin, straight socket<br>M8, 3-pin    | 0.5 m                 | 541346   | NEBU-M8G3-K-0.5-M8G3 |
|                                                                                     |                                                          | 1.0 m                 | 541347   | NEBU-M8G3-K-1-M8G3   |
|                                                                                     |                                                          | 2.5 m                 | 541348   | NEBU-M8G3-K-2.5-M8G3 |
|                                                                                     |                                                          | 5.0 m                 | 541349   | NEBU-M8G3-K-5-M8G3   |

# AS-interface® components

CPV valve terminals – Accessories

FESTO

| Ordering data                                                                       |                                                                     |         |          |                         |
|-------------------------------------------------------------------------------------|---------------------------------------------------------------------|---------|----------|-------------------------|
|                                                                                     | Description                                                         |         | Part No. | Type                    |
| Miscellaneous                                                                       |                                                                     |         |          |                         |
|    | Primary switched mode, modular power supply<br>24 V DC power supply | 5 A     | 2247681  | CACN-3A-1-5             |
|                                                                                     |                                                                     | 10 A    | 2247682  | CACN-3A-1-10            |
|    | Addressing device (power supply plug included in scope of delivery) |         | 18959    | ASI-PRG-ADR             |
|    | Addressing cable                                                    |         | 18960    | KASI-ADR                |
|    | AS-interface input module for 8 inputs M8                           |         | 542124   | ASI-8DI-M8-3POL         |
|    | AS-interface input/output module for 4 inputs/3 outputs M12         |         | 542125   | ASI-4DI3DO-M12X2-5POL-Z |
|   | Inscription labels 6x10mm in frames (64pieces)                      |         | 18576    | IBS 6x10                |
|                                                                                     | Inscription labels 9x20mm in frames (20 pieces)                     |         | 18182    | IBS 9x20                |
|  | H-rail to EN 60715                                                  |         | 35430    | NRH-35-2000             |
|  | Mounting for H-rail                                                 |         | 162556   | CPV10/14-VI-BG-NRH-35   |
|                                                                                     |                                                                     |         | 163291   | CPV18-VI-BG-NRH-35      |
| User's manual                                                                       |                                                                     |         |          |                         |
|  | CPV Pneumatics Description                                          | German  | 165100   | P.BE-CPV-DE             |
|                                                                                     |                                                                     | English | 165200   | P.BE-CPV-EN             |
|                                                                                     |                                                                     | French  | 165130   | P.BE-CPV-FR             |
|                                                                                     |                                                                     | Italian | 165160   | P.BE-CPV-IT             |
|                                                                                     |                                                                     | Spanish | 165230   | P.BE-CPV-ES             |



## MPA-S valve terminals with AS-interface – Valve configuration options

MPA valve terminals with AS-interface can be flexibly configured with a wide range of valves. The system supports a maximum of 8 outputs (solenoid coils) and 8 inputs per valve terminal. This gives the following basic valve configuration options (see tables on following page).



### Note

Please follow the link below for more details on the various pneumatic functions.

➔ Internet: mpa-s

### General data

- Solutions with integrated inputs
- Width 10 or 20 mm
- With or without 24 V DC auxiliary power supply for solenoid coils (EMERGENCY-STOP circuitry) in the case of the 4I/4O version. The auxiliary power supply is always integrated in the version with 8 inputs and cannot be subsequently switched off using the DIL switch
- Selectable bus connection technology
  - Flat cable for AS-interface with 4I/4O version
  - 4-pin M12 round plug<sup>1)</sup> with 4I/4O and 8I/8O version
- Selectable addressing
  - Via bus connection (M12 or flat cable)

### Versions

- 2 to 8 valves, freely configurable
- With 4 or 8 inputs
- M12, M8, quick connection, tension spring or Sub-D connection technology
- Separating seals for the creation of pressure zones
- Suitable for vacuum
- Subsequent extensions either
  - via unused valve positions
  - by converting the valve terminal

### Application

- Flexible and cost-effective connection of 2 or 8 valves (max. 8 solenoid coils) with input feedback
- Decentralised machine and system structures, for example
  - in handling technology
  - in conveyor technology
  - in the packaging industry
  - in sorting systems
  - suitable for energy chains thanks to connection via round cables

1) Suitable cable distributor from flat cable to M12 ➔ 46

| Types of valve terminal with AS-interface |        |                |        |                  |                           |                                            |    |       |       |
|-------------------------------------------|--------|----------------|--------|------------------|---------------------------|--------------------------------------------|----|-------|-------|
| Type                                      | Valves | Solenoid coils | Inputs | Conforms to SPEC | Extended addressing range | Auxiliary power supply can be disconnected |    | Width |       |
|                                           |        |                |        |                  |                           | Yes                                        | No | 10 mm | 20 mm |
| VMPA-ASI-EPL-E-4E4A-Z                     | 4      | 4              | 4      | 2.1              | –                         | ■                                          | –  | ■     | ■     |
| VMPA-ASI-EPL-G-4E4A-Z                     | 4      | 4              | 4      | 2.1              | –                         | ■                                          | –  | ■     | ■     |
| VMPA-ASI-EPL-EU-4E4A-Z                    | 4      | 4              | 4      | 2.1              | –                         | ■                                          | –  | ■     | ■     |
| VMPA-ASI-EPL-GU-4E4A-Z                    | 4      | 4              | 4      | 2.1              | –                         | ■                                          | –  | ■     | ■     |
| VMPA-ASI-EPL-E-8E8A-Z                     | 8      | 8              | 8      | 2.1              | –                         | –                                          | ■  | ■     | ■     |
| VMPA-ASI-EPL-G-8E8A-Z                     | 8      | 8              | 8      | 2.1              | –                         | –                                          | ■  | ■     | ■     |
| VMPA-ASI-EPL-EU-8E8A-Z                    | 8      | 8              | 8      | 2.1              | –                         | –                                          | ■  | ■     | ■     |
| VMPA-ASI-EPL-GU-8E8A-Z                    | 8      | 8              | 8      | 2.1              | –                         | –                                          | ■  | ■     | ■     |
| VMPA-ASI-EPL-E-8E8A-CE                    | 8      | 8              | 8      | 3.0              | ■                         | –                                          | ■  | ■     | ■     |
| VMPA-ASI-EPL-G-8E8A-CE                    | 8      | 8              | 8      | 3.0              | ■                         | –                                          | ■  | ■     | ■     |
| VMPA-ASI-EPL-EU-8E8A-CE                   | 8      | 8              | 8      | 3.0              | ■                         | –                                          | ■  | ■     | ■     |
| VMPA-ASI-EPL-GU-8E8A-CE                   | 8      | 8              | 8      | 3.0              | ■                         | –                                          | ■  | ■     | ■     |

| Permissible combinations in valve position allocation |         |   |   |   |
|-------------------------------------------------------|---------|---|---|---|
| Type                                                  | Slave n |   |   |   |
|                                                       | 0       | 1 | 2 | 3 |
| 4l/4O MPA1 - only M<br>(up to 4 valves per sub-base)  | M       | M | M | M |
|                                                       | M       | M | M | L |
|                                                       | M       | M | L | L |
|                                                       | M       | L | L | L |
| 4l/4O MPA2<br>(2 valves per sub-base)                 | M       | M | M | M |
|                                                       | J       | M | – | – |
|                                                       | M       | J | – | – |
|                                                       | J       | J | – | – |

| Permissible combinations in valve position allocation |                        |     |     |     |     |     |     |     |
|-------------------------------------------------------|------------------------|-----|-----|-----|-----|-----|-----|-----|
| Type                                                  | Slave n plus slave n+1 |     |     |     |     |     |     |     |
|                                                       | 0                      | 1   | 2   | 3   | 4   | 5   | 6   | 7   |
| 8l/8O MPA1<br>(up to 4 valves per sub-base)           | M                      | M   | M   | M   | M   | M   | M   | M   |
|                                                       | M                      | M   | M   | L   | M   | M   | M   | L   |
|                                                       | J                      | J   | J   | J   | –   | –   | –   | –   |
|                                                       | ...                    | ... | ... | ... | ... | ... | ... | ... |
|                                                       | J                      | J   | J   | J   | –   | –   | –   | –   |
|                                                       | J                      | J   | J   | M   | –   | –   | –   | –   |
|                                                       | J                      | J   | M   | M   | –   | –   | –   | –   |
|                                                       | ...                    | ... | ... | ... | ... | ... | ... | ... |
|                                                       | J                      | J   | L   | L   | –   | –   | –   | –   |
|                                                       | J                      | J   | L   | L   | –   | –   | –   | –   |
| 8l/8O MPA2<br>(2 valves per sub-base)                 | M                      | M   | M   | M   | M   | M   | M   | M   |
|                                                       | M                      | M   | M   | L   | M   | M   | M   | L   |
|                                                       | ...                    | ... | ... | ... | ... | ... | ... | ... |
|                                                       | J                      | J   | J   | J   | –   | –   | –   | –   |
|                                                       | J                      | J   | J   | M   | –   | –   | –   | –   |
|                                                       | J                      | J   | M   | M   | –   | –   | –   | –   |
|                                                       | ...                    | ... | ... | ... | ... | ... | ... | ... |
|                                                       | J                      | J   | M   | M   | M   | M   | –   | –   |
|                                                       | J                      | J   | M   | M   | M   | L   | –   | –   |
|                                                       | ...                    | ... | ... | ... | ... | ... | ... | ... |
|                                                       | M                      | M   | M   | M   | J   | J   | –   | –   |
|                                                       | M                      | M   | M   | M   | J   | J   | –   | –   |
|                                                       | M                      | M   | M   | M   | J   | J   | –   | –   |


# AS-interface® components

MPA-S valve terminal – Connection technology and addressing


FESTO

## Installation: Selectable connection technology for AS-interface

### Support for flat cables




- Straightforward cabling with flat cables in protected areas
- Fast system of installation with standard AS-interface cables
- Standard installation at the AS-interface with yellow flat cables is possible with the 4I/40 MPA-S version




Standard installation at the AS-interface flat cable

### Support for round cables



Local round cable wiring system for areas subjected to consistently high stress:


- Permanently high humidity
- Need for flexible cabling using one cable
- Use in energy chains with highly flexible cables



- 1 Pre-assembled M12 round cable, 1 m, polyurethane
- 2 Selectable cable for additional slave, for example highly flexible cable for energy chains or PVC cable for applications requiring resistance to detergents


## Addressing

### Addressing device



- The addressing device to SPEC V2.1 can be used to scan the AS-interface from any point in the network. At all connected stations
- slave addresses can be read/changed
  - ID and IO codes can be read out
  - parameters can be read/changed
  - input/output data can be read and written (setting outputs)
  - error messages can be read out and quickly recognised

### AS-interface connections




- 1 M12 plug for AS-interface and incoming auxiliary supply
- 2 M12 socket for AS-interface and outgoing auxiliary supply

# AS-interface® components

MPA-S valve terminal – Connection technology and addressing

FESTO

## AS-interface flat cable distributor to round cable



### Alternative connection concepts

- AS-interface connection technology for yellow and optionally for black flat cables
- Passive conversion of the signals to M12 socket and round cable via M12 socket
- Pre-assembled round cable, PUR, 1 m long
- Alternatively PVC extension cable, 2.5 and 5 m, via additional M12 socket

### Selecting the cable

Optimised connection technologies at the AS-interface can be easily realised by selecting the right cable.


- Flat cables for all standard applications with installation-saving insulation displacement technology
- Round cables for applications with differing requirements, for example:
  - Energy chains with small radii and further requirements for highly flexible cables

- Applications with consistently high humidity
- Applications involving frequent cleaning and requiring cables resistant to detergents (PUR, PVC or other cables)
- Cabling systems using standard components (M12) preferred

### Easy to mount

- Direct mounting on a wall or machine frame

## Supplementary compact I/O modules



The valve terminals MPA-S can be supplemented with the compact I/O modules. The following are available:

- 8 inputs M8
- 4 inputs/3 outputs M12

# AS-interface® components

Key features – Display and operation

FESTO

## Display and operation

Each valve solenoid coil is allocated an LED which indicates its signal status.

- Indicator 12 shows the switching status of the coil for output 2
- Indicator 14 shows the switching status of the coil for output 4

### Manual override

The manual override (MO) enables the valve to be actuated when not electrically activated or energised. The valve is activated by pushing the manual override. The set switching status can also be locked by turning

the manual override (code R or as accessory).


Alternatives:

- A cover (code N or as accessory) can be fitted over the manual override to prevent it from being locked. The

manual override can then only be activated by pushing it.

- A cover (code V) can be fitted over the manual override to prevent it from being accidentally activated.

## Pneumatic connection and control elements




- 1 Flat plate silencer exhaust air 3/5
- 2 Manual override (for each pilot solenoid coil, non-detenting or detenting)
- 3 Adjusting knob for optional pressure regulator plate
- 4 Inscription label holder for sub-base
- 5 Working ports 2 and 4, for each valve position
- 6 Supply port 1
- 7 Pressure gauge (optional)
- 8 Ports 12 and 14 for supplying external pilot air

-  Note

A manually actuated valve (manual override) cannot be reset electrically. Conversely, an electrically actuated valve cannot be reset using the mechanical manual override.

## Electrical connection and display components AS-interface



- 1 M12 socket AS-interface bus and additional supply (AS-i Out)
- 2 M12 plug AS-interface bus and additional supply (AS-i In)
- 3 Earth terminal
- 4 Status LEDs inputs
- 5 Status LEDs AS-interface
- 6 Diagnostic LEDs valves







| General technical data                          |                                                    |                                                                                 |                                                                                 |                                                                                 |
|-------------------------------------------------|----------------------------------------------------|---------------------------------------------------------------------------------|---------------------------------------------------------------------------------|---------------------------------------------------------------------------------|
| Type                                            | VMPA-...-4E4A-Z                                    |                                                                                 | VMPA-...-8E8A-Z                                                                 | VMPA-...-8E8A-CE                                                                |
| Part No.                                        | Order via order code/valve terminal configurator   |                                                                                 |                                                                                 |                                                                                 |
| Valves                                          | Number of solenoid coils                           | 4                                                                               |                                                                                 | 8                                                                               |
|                                                 | Valve width [mm]                                   | 10/20                                                                           |                                                                                 |                                                                                 |
|                                                 | External power supply<br>24 V DC                   | Set using DIL switch                                                            |                                                                                 | Yes                                                                             |
| Inputs                                          | No. of digital inputs                              | 4                                                                               |                                                                                 | 8                                                                               |
|                                                 | Connection technology                              | 5-pin M12, 3-pin M8, Harax, CageClamp, Sub-D                                    |                                                                                 |                                                                                 |
|                                                 | Sensor supply via AS-interface                     | Short circuit and overload proof                                                |                                                                                 |                                                                                 |
|                                                 | Sensor connection                                  | 2-wire and 3-wire sensors                                                       |                                                                                 |                                                                                 |
|                                                 | Type                                               | IEC 1131-2, type 02                                                             |                                                                                 |                                                                                 |
|                                                 | Input circuitry                                    | PNP (positive switching)                                                        |                                                                                 |                                                                                 |
| AS-interface connection                         | Connection technology                              | M12 connection <sup>2)</sup>                                                    |                                                                                 |                                                                                 |
|                                                 | Voltage range [V DC]                               | 26.5 ... 31.6, reverse polarity protected                                       |                                                                                 |                                                                                 |
|                                                 | Residual ripple [mVss]                             | 20                                                                              |                                                                                 |                                                                                 |
|                                                 | Current consumption of inputs                      | Without auxiliary power supply                                                  | With auxiliary power supply                                                     | With auxiliary power supply                                                     |
|                                                 | Basic electronic load                              | ≤25                                                                             | ≤25                                                                             | ≤25                                                                             |
|                                                 | Total input current                                | 350                                                                             | 350                                                                             | 350                                                                             |
|                                                 | Total output current (valves incl. LED) [mA]       | MPA1: 270<br>MPA2: 533                                                          | MPA1: 540<br>MPA2: 1065                                                         | MPA1: 540<br>MPA2: 1065                                                         |
| Load voltage connection                         | Connection technology                              | M12 connection <sup>2)</sup>                                                    |                                                                                 |                                                                                 |
|                                                 | Voltage range [V DC]                               | 21.6 ... 26.4                                                                   |                                                                                 |                                                                                 |
|                                                 | Residual ripple [Vss]                              | 4                                                                               |                                                                                 |                                                                                 |
| Current consumption of valves per solenoid coil | • Max. starting current (at 24 V) [mA]             | MPA1: ≤80<br>MPA2: ≤100                                                         |                                                                                 |                                                                                 |
|                                                 | • Following current reduction (approx. 25 ms) [mA] | MPA1: ≤25<br>MPA2: ≤20                                                          |                                                                                 |                                                                                 |
| LED displays                                    | ASI-LED                                            | Green                                                                           |                                                                                 |                                                                                 |
|                                                 | AUX-PWR-LED                                        | Green                                                                           |                                                                                 |                                                                                 |
|                                                 | FAULT-LED                                          | Red                                                                             |                                                                                 |                                                                                 |
|                                                 | Inputs                                             | Green                                                                           |                                                                                 |                                                                                 |
|                                                 | Valves                                             | Yellow                                                                          |                                                                                 |                                                                                 |
| General data                                    | Protection class (to EN 60529)                     | IP65 (fully assembled)                                                          |                                                                                 |                                                                                 |
|                                                 | Temperature range [°C]                             | Operation: -5 ... +50; storage/transport: -20 ... +40                           |                                                                                 |                                                                                 |
|                                                 | Relative air humidity                              | Max. 90% at 40 °C                                                               |                                                                                 |                                                                                 |
|                                                 | Materials                                          | Die-cast aluminium, PA                                                          |                                                                                 |                                                                                 |
|                                                 | Note on materials                                  | RoHS-compliant                                                                  |                                                                                 |                                                                                 |
|                                                 | Dimensions                                         | ➔ 45                                                                            |                                                                                 |                                                                                 |
|                                                 | Weight [g]                                         | 360                                                                             |                                                                                 |                                                                                 |
| AS-interface data                               | ID code                                            | ID = F <sub>H</sub> ; ID1 = F <sub>H</sub> <sup>1)</sup> ; ID2 = E <sub>H</sub> | ID = F <sub>H</sub> ; ID1 = F <sub>H</sub> <sup>1)</sup> ; ID2 = E <sub>H</sub> | ID = A <sub>H</sub> ; ID1 = F <sub>H</sub> <sup>1)</sup> ; ID2 = E <sub>H</sub> |
|                                                 | IO code                                            | 7 <sub>H</sub>                                                                  | 7 <sub>H</sub>                                                                  | 7 <sub>H</sub>                                                                  |
|                                                 | Profile                                            | S-7.FE                                                                          | S-7.FE                                                                          | S-7.A.E                                                                         |
|                                                 | Addressing range                                   | 1 ... 31                                                                        | 1 ... 31                                                                        | 1A ... 31A, 1B ... 31B                                                          |







1) Factory setting, set to 0<sub>H</sub> by some programming devices (Spec. V2.1) when addressing the slave

2) Suitable cable distributor from flat cable to M12 ➔ 46

| ATEX                                    |                                             |
|-----------------------------------------|---------------------------------------------|
| Type                                    | MPA-ASI-VI                                  |
| ATEX category gas                       | II 3 G                                      |
| Ex-ignition protection type gas         | Ex nA IIC T4 X Gc                           |
| Explosion-proof temperature rating [°C] | -5 ≤ Ta ≤ +50                               |
| CE mark (see declaration of conformity) | To EU Explosion Protection Directive (ATEX) |

| Combinations of connection blocks and electronics modules for inputs |          |               |               |
|----------------------------------------------------------------------|----------|---------------|---------------|
| Connection blocks                                                    | Part No. | VMPA-...-8E8A | VMPA-...-4E4A |
| CPX-AB-4-M12X2-5POL                                                  | 195704   | ■             | ■             |
| CPX-AB-8-M8-3POL                                                     | 195706   | ■             | ■             |
| CPX-AB-8-KL-4POL                                                     | 195708   | ■             | ■             |
| CPX-AB-1-SUB-BU-25POL                                                | 525676   | ■             | ■             |
| CPX-AB-4-HAR-4POL                                                    | 525636   | ■             | ■             |

| Pin allocation                                                                      |                                                                                     |                                                                                     |                                                                                                                 |                                                                                                                 |                                                                                                                 |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|
| Connection block inputs                                                             |                                                                                     | VMPA-...-8E8A                                                                       |                                                                                                                 | VMPA-...-4E4A                                                                                                   |                                                                                                                 |
| CPX-AB-4-M12X2-5P-M3                                                                |                                                                                     |                                                                                     |                                                                                                                 |                                                                                                                 |                                                                                                                 |
|   |    |    | X1.1: 24 V <sub>SEN</sub><br>X1.2: Input x+1<br>X1.3: 0 V <sub>SEN</sub><br>X1.4: Input x<br>X1.5: FE (earth)   | X3.1: 24 V <sub>SEN</sub><br>X3.2: Input x+5<br>X3.3: 0 V <sub>SEN</sub><br>X3.4: Input x+4<br>X3.5: FE (earth) | X1.1: 24 V <sub>SEN</sub><br>X1.2: Input x+1<br>X1.3: 0 V <sub>SEN</sub><br>X1.4: Input x<br>X1.5: FE (earth)   |
|                                                                                     |   |   | X2.1: 24 V <sub>SEN</sub><br>X2.2: Input x+3<br>X2.3: 0 V <sub>SEN</sub><br>X2.4: Input x+2<br>X2.5: FE (earth) | X4.1: 24 V <sub>SEN</sub><br>X4.2: Input x+7<br>X4.3: 0 V <sub>SEN</sub><br>X4.4: Input x+6<br>X4.5: FE (earth) | X3.1: 24 V <sub>SEN</sub><br>X3.2: Input x+3<br>X3.3: 0 V <sub>SEN</sub><br>X3.4: Input x+2<br>X3.5: FE (earth) |
|                                                                                     |                                                                                     |                                                                                     |                                                                                                                 |                                                                                                                 |                                                                                                                 |
|                                                                                     |                                                                                     |                                                                                     |                                                                                                                 |                                                                                                                 |                                                                                                                 |
| CPX-AB-8-M8-3P-M3                                                                   |                                                                                     |                                                                                     |                                                                                                                 |                                                                                                                 |                                                                                                                 |
|  |  |  | X1.1: 24 V <sub>SEN</sub><br>X1.3: 0 V <sub>SEN</sub><br>X1.4: Input x                                          | X5.1: 24 V <sub>SEN</sub><br>X5.3: 0 V <sub>SEN</sub><br>X5.4: Input x+4                                        | X1.1: 24 V <sub>SEN</sub><br>X1.3: 0 V <sub>SEN</sub><br>X1.4: Input x                                          |
|                                                                                     |  |  | X2.1: 24 V <sub>SEN</sub><br>X2.3: 0 V <sub>SEN</sub><br>X2.4: Input x+1                                        | X6.1: 24 V <sub>SEN</sub><br>X6.3: 0 V <sub>SEN</sub><br>X6.4: Input x+5                                        | X2.1: 24 V <sub>SEN</sub><br>X2.3: 0 V <sub>SEN</sub><br>X2.4: Input x+1                                        |
|                                                                                     |  |  |                                                                                                                 |                                                                                                                 |                                                                                                                 |
|                                                                                     |  |  | X3.1: 24 V <sub>SEN</sub><br>X3.3: 0 V <sub>SEN</sub><br>X3.4: Input x+2                                        | X7.1: 24 V <sub>SEN</sub><br>X7.3: 0 V <sub>SEN</sub><br>X7.4: Input x+6                                        | X3.1: 24 V <sub>SEN</sub><br>X3.3: 0 V <sub>SEN</sub><br>X3.4: Input x+1                                        |
|                                                                                     |                                                                                     |                                                                                     | X4.1: 24 V <sub>SEN</sub><br>X4.3: 0 V <sub>SEN</sub><br>X4.4: Input x+3                                        | X8.1: 24 V <sub>SEN</sub><br>X8.3: 0 V <sub>SEN</sub><br>X8.4: Input x+7                                        | X4.1: 24 V <sub>SEN</sub><br>X4.3: 0 V <sub>SEN</sub><br>X4.4: n.c.                                             |

| Pin allocation                                                                      |                                                                                     |                                                                                                                                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                                                                                                                                                                          |                                                                                                                                                                                                                                                                                                                                                                                                   |                                                                                                                                                                                                                                                                                                                                                                                                     |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Connection block inputs                                                             |                                                                                     | VMPA-...-8E8A                                                                                                                                                                                                                                                                                                                                                                                          |                                                                                                                                                                                                                                                                                                                                                                                                          | VMPA-...-4E4A                                                                                                                                                                                                                                                                                                                                                                                     |                                                                                                                                                                                                                                                                                                                                                                                                     |
| CPX-AB-8-KL-4P-M3                                                                   |                                                                                     |                                                                                                                                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                                                                                                                                                                          |                                                                                                                                                                                                                                                                                                                                                                                                   |                                                                                                                                                                                                                                                                                                                                                                                                     |
|    |    | X1.0: 24 V <sub>SEN</sub><br>X1.1: 0 V <sub>SEN</sub><br>X1.2: Input x<br>X1.3: FE (earth)<br><br>X2.0: 24 V <sub>SEN</sub><br>X2.1: 0 V <sub>SEN</sub><br>X2.2: Input x+1<br>X2.3: FE (earth)<br><br>X3.0: 24 V <sub>SEN</sub><br>X3.1: 0 V <sub>SEN</sub><br>X3.2: Input x+2<br>X3.3: FE (earth)<br><br>X4.0: 24 V <sub>SEN</sub><br>X4.1: 0 V <sub>SEN</sub><br>X4.2: Input x+3<br>X4.3: FE (earth) | X5.0: 24 V <sub>SEN</sub><br>X5.1: 0 V <sub>SEN</sub><br>X5.2: Input x+4<br>X5.3: FE (earth)<br><br>X6.0: 24 V <sub>SEN</sub><br>X6.1: 0 V <sub>SEN</sub><br>X6.2: Input x+5<br>X6.3: FE (earth)<br><br>X7.0: 24 V <sub>SEN</sub><br>X7.1: 0 V <sub>SEN</sub><br>X7.2: Input x+6<br>X7.3: FE (earth)<br><br>X8.0: 24 V <sub>SEN</sub><br>X8.1: 0 V <sub>SEN</sub><br>X8.2: Input x+7<br>X8.3: FE (earth) | X1.0: 24 V <sub>SEN</sub><br>X1.1: 0 V <sub>SEN</sub><br>X1.2: Input x<br>X1.3: FE (earth)<br><br>X2.0: 24 V <sub>SEN</sub><br>X2.1: 0 V <sub>SEN</sub><br>X2.2: Input x+1<br>X2.3: FE (earth)<br><br>X3.0: 24 V <sub>SEN</sub><br>X3.1: 0 V <sub>SEN</sub><br>X3.2: Input x+1<br>X3.3: FE (earth)<br><br>X4.0: 24 V <sub>SEN</sub><br>X4.1: 0 V <sub>SEN</sub><br>X4.2: n.c.<br>X4.3: FE (earth) | X5.0: 24 V <sub>SEN</sub><br>X5.1: 0 V <sub>SEN</sub><br>X5.2: Input x+2<br>X5.3: FE (earth)<br><br>X6.0: 24 V <sub>SEN</sub><br>X6.1: 0 V <sub>SEN</sub><br>X6.2: Input x+3<br>X6.3: FE (earth)<br><br>X7.0: 24 V <sub>SEN</sub><br>X7.1: 0 V <sub>SEN</sub><br>X7.2: Input x+3<br>X7.3: FE (earth)<br><br>X8.0: 24 V <sub>SEN</sub><br>X8.1: 0 V <sub>SEN</sub><br>X8.2: n.c.<br>X8.3: FE (earth) |
| CPX-AB-1-SUB-BU-25P-M3                                                              |                                                                                     |                                                                                                                                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                                                                                                                                                                          |                                                                                                                                                                                                                                                                                                                                                                                                   |                                                                                                                                                                                                                                                                                                                                                                                                     |
|  |  | 1: Input x<br>2: Input x+1<br>3: Input x+2<br>4: Input x+3<br>5: 24 V <sub>SEN</sub><br>6: 0 V <sub>SEN</sub><br>7: 24 V <sub>SEN</sub><br>8: 0 V <sub>SEN</sub><br>9: 24 V <sub>SEN</sub><br>10: 24 V <sub>SEN</sub><br>11: 0 V <sub>SEN</sub><br>12: 0 V <sub>SEN</sub><br>13: FE (earth)                                                                                                            | 14: Input x+4<br>15: Input x+5<br>16: Input x+6<br>17: Input x+7<br>18: 24 V <sub>SEN</sub><br>19: 24 V <sub>SEN</sub><br>20: 24 V <sub>SEN</sub><br>21: 24 V <sub>SEN</sub><br>22: 0 V <sub>SEN</sub><br>23: 0 V <sub>SEN</sub><br>24: 0 V <sub>SEN</sub><br>25: FE (earth)<br>Socket: FE                                                                                                               | 1: Input x<br>2: Input x+1<br>3: Input x+1<br>4: n.c.<br>5: 24 V <sub>SEN</sub><br>6: 0 V <sub>SEN</sub><br>7: 24 V <sub>SEN</sub><br>8: 0 V <sub>SEN</sub><br>9: 24 V <sub>SEN</sub><br>10: 24 V <sub>SEN</sub><br>11: 0 V <sub>SEN</sub><br>12: 0 V <sub>SEN</sub><br>13: FE (earth)                                                                                                            | 14: Input x+2<br>15: Input x+3<br>16: Input x+3<br>17: n.c.<br>18: 24 V <sub>SEN</sub><br>19: 24 V <sub>SEN</sub><br>20: 24 V <sub>SEN</sub><br>21: 24 V <sub>SEN</sub><br>22: 0 V <sub>SEN</sub><br>23: 0 V <sub>SEN</sub><br>24: 0 V <sub>SEN</sub><br>25: FE (earth)<br>Socket: FE                                                                                                               |
| CPX-AB-4-HAR-4P-M3                                                                  |                                                                                     |                                                                                                                                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                                                                                                                                                                          |                                                                                                                                                                                                                                                                                                                                                                                                   |                                                                                                                                                                                                                                                                                                                                                                                                     |
|  |  | X1.1: 24 V <sub>SEN</sub><br>X1.2: Input x+1<br>X1.3: 0 V <sub>SEN</sub><br>X1.4: Input x<br><br>X2.1: 24 V <sub>SEN</sub><br>X2.2: Input x+3<br>X2.3: 0 V <sub>SEN</sub><br>X2.4: Input x+2                                                                                                                                                                                                           | X3.1: 24 V <sub>SEN</sub><br>X3.2: Input x+5<br>X3.3: 0 V <sub>SEN</sub><br>X3.4: Input x+4<br><br>X4.1: 24 V <sub>SEN</sub><br>X4.2: Input x+7<br>X4.3: 0 V <sub>SEN</sub><br>X4.4: Input x+6                                                                                                                                                                                                           | X1.1: 24 V <sub>SEN</sub><br>X1.2: Input x+1<br>X1.3: 0 V <sub>SEN</sub><br>X1.4: Input x<br><br>X2.1: 24 V <sub>SEN</sub><br>X2.2: n.c.<br>X2.3: 0 V <sub>SEN</sub><br>X2.4: Input x+1                                                                                                                                                                                                           | X3.1: 24 V <sub>SEN</sub><br>X3.2: Input x+3<br>X3.3: 0 V <sub>SEN</sub><br>X3.4: Input x+2<br><br>X4.1: 24 V <sub>SEN</sub><br>X4.2: n.c.<br>X4.3: 0 V <sub>SEN</sub><br>X4.4: Input x+3                                                                                                                                                                                                           |


# AS-interface® components

MPA-S valve terminal – Dimensions

FESTO

## Dimensions





Download CAD data → [www.festo.com](http://www.festo.com)



# AS-interface® components

MPA-S valve terminal – Accessories








**FESTO**

| Ordering data                                                                       |                                                                                  |                             |          |                   |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------|-----------------------------|----------|-------------------|
|                                                                                     | Description                                                                      |                             | Part No. | Type              |
| Bus connection                                                                      |                                                                                  |                             |          |                   |
|    | AS-interface flat cable, yellow                                                  | 100 m                       | 18940    | KASI-1,5-Y-100    |
|                                                                                     | AS-interface flat cable, black                                                   | 100 m                       | 18941    | KASI-1,5-Z-100    |
|    | Flat cable blanking plug                                                         |                             | 196090   | ASI-SD-FK-BL      |
|    | AS-interface flat cable distributor                                              | Parallel cable              | 18786    | ASI-KVT-FK        |
|    | AS-interface flat cable distributor                                              | Symmetrical cable           | 18797    | ASI-KVT-FK-S      |
|    | Cable cap for flat cable (scope of delivery 50 pieces)                           |                             | 18787    | ASI-KK-FK         |
|   | Cable sleeve (scope of delivery 20 pieces)                                       |                             | 165593   | ASI-KT-FK         |
|  | Socket M12, 4-pin                                                                | For AS-interface flat cable | 18789    | ASI-SD-PG-M12     |
|  | Socket M12, 5-pin                                                                | For round cable             | 18324    | FBSD-GD-9-5POL    |
| Cable distributor                                                                   |                                                                                  |                             |          |                   |
|  | AS-Interface data to socket M12, 4-pin                                           |                             | 572225   | NEFU-X22F-M12G4   |
|  | AS-Interface data and load voltage supply to socket M12, 4-pin                   |                             | 572226   | NEFU-X24F-M12G4   |
|  | AS-Interface data and load voltage supply to socket M12, 4-pin, cable length 1 m |                             | 572227   | NEFU-X24F-1-M12G4 |
| DUO plug                                                                            |                                                                                  |                             |          |                   |
|  | Plug M12 for 2 sensor cables                                                     | 4-pin, PG11                 | 18779    | SEA-GS-11-DUO     |
|                                                                                     |                                                                                  | 5-pin, PG11                 | 192010   | SEA-5GS-11-DUO    |

# AS-interface® components

MPA-S valve terminal – Accessories







**FESTO**

| Ordering data                                                                       |                                                                    |                               |          |                            |
|-------------------------------------------------------------------------------------|--------------------------------------------------------------------|-------------------------------|----------|----------------------------|
|                                                                                     | Description                                                        |                               | Part No. | Type                       |
| Sensor plugs                                                                        |                                                                    |                               |          |                            |
|    | Straight sensor plug                                               | M12, 4-pin, PG7               | 18666    | SEA-GS-7                   |
|    | Straight sensor plug                                               | M12, 5-pin, PG7               | 175487   | SEA-M12-5GS-PG7            |
|    | Straight sensor plug                                               | M12, PG9 connector            | 18778    | SEA-GS-9                   |
|    | Straight sensor plug for cable Ø 2.5 mm                            | M12, 4-pin                    | 192008   | SEA-4GS-7-2,5              |
|                                                                                     | Straight sensor plug                                               | M8, screw-in, 3-pin           | 192009   | SEA-3GS-M8-S               |
|    | Straight sensor plug                                               | M8, solderable, 3-pin         | 18696    | SEA-GS-M8                  |
|    | Harax sensor plug                                                  | 4-pin                         | 525928   | SEA-GS-HAR-4POL            |
|   | Sub-D plug                                                         | 25-pin                        | 527522   | SD-SUB-D-ST25              |
|  | Cover cap (scope of delivery 10 pieces)                            | M12                           | 165592   | ISK-M12                    |
|                                                                                     |                                                                    | M8                            | 177672   | ISK-M8                     |
| Connecting cables                                                                   |                                                                    |                               |          |                            |
|  | Modular system for connecting cables<br>➔ Internet: nebu           |                               | –        | NEBU-...                   |
|                                                                                     | Straight plug M8, 3-pin, straight socket<br>M8, 3-pin              | 0.5 m                         | 541346   | NEBU-M8G3-K-0.5-M8G3       |
|                                                                                     |                                                                    | 1.0 m                         | 541347   | NEBU-M8G3-K-1-M8G3         |
|                                                                                     |                                                                    | 2.5 m                         | 541348   | NEBU-M8G3-K-2.5-M8G3       |
|                                                                                     |                                                                    | 5.0 m                         | 541349   | NEBU-M8G3-K-5-M8G3         |
|                                                                                     | Straight plug M12, 4-pin, straight socket<br>M12, 5-pin            | 0.5 m                         | 8000208  | NEBU-M12G5-K-0.5-M12G4     |
| T-type plug connector                                                               |                                                                    |                               |          |                            |
|  | Plug M12, A-coded, 4-pin                                           | 2x socket M12, A-coded, 5-pin | 8005310  | NEDY-L2R1-V1-M12G5-N-M12G4 |
|                                                                                     |                                                                    | 2x socket M8, A-coded, 3-pin  | 8005311  | NEDY-L2R1-V1-M8G3-N-M12G4  |
|  | Modular system for sensor/actuator distributor<br>➔ Internet: nedy |                               | –        | NEDY-...                   |

# AS-interface® components

MPA-S valve terminal – Accessories

**FESTO**

| Ordering data                                                                       |                                                                                  |         |          |                         |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------|---------|----------|-------------------------|
|                                                                                     | Description                                                                      |         | Part No. | Type                    |
| Miscellaneous                                                                       |                                                                                  |         |          |                         |
|    | Primary switched mode, modular power supply<br>24 V DC power supply              | 5 A     | 2247681  | CACN-3A-1-5             |
|                                                                                     |                                                                                  | 10 A    | 2247682  | CACN-3A-1-10            |
|    | Addressing device (power supply plug included in scope of delivery)              |         | 18959    | ASI-PRG-ADR             |
|    | Addressing cable                                                                 |         | 18960    | KASI-ADR                |
|    | AS-interface input module for 8 inputs M8, compact                               |         | 542124   | ASI-8DI-M8-3POL         |
|    | AS-interface input/output module for 4 inputs/3 outputs M12, compact             |         | 542125   | ASI-4DI3DO-M12X2-5POL-Z |
|   | Inscription labels 6x10mm in frames (64pieces)                                   |         | 18576    | IBS 6x10                |
|  | Inscription label holder for connection block, transparent, for paper foil label |         | 533362   | VMPA1-ST-1-4            |
|                                                                                     | Inscription label holder for connection block, 4-fold, for IBS 6x10              |         | 544384   | VMPA1 ST 2-4            |
|  | H-rail to EN 60715                                                               |         | 35430    | NRH-35-2000             |
|  | H-rail mounting                                                                  |         | 526032   | CPX-CPA-BG-NRH          |
|  | Mounting bracket                                                                 |         | 534416   | VMPA-BG-RW              |
|                                                                                     |                                                                                  |         |          |                         |
| User's manual                                                                       |                                                                                  |         |          |                         |
|  | MPA-S Pneumatics Description                                                     | German  | 534240   | P.BE-MPA-DE             |
|                                                                                     |                                                                                  | English | 534241   | P.BE-MPA-EN             |
|                                                                                     |                                                                                  | French  | 534243   | P.BE-MPA-FR             |
|                                                                                     |                                                                                  | Italian | 534244   | P.BE-MPA-IT             |
|                                                                                     |                                                                                  | Spanish | 534242   | P.BE-MPA-ES             |

# AS-interface® components

VTSA/VTSA-F valve terminal

FESTO



## VTSA/VTSA-F valve terminals with AS-interface – Valve configuration options

VTSA/VTSA-F valve terminals with AS-interface can be flexibly configured with a wide range of valves. The system supports a maximum of 8 outputs (solenoid coils) and 8 inputs per valve terminal. This gives the following basic valve configuration options (see tables on following page).

### Note

Please follow the link below for more details on the various pneumatic functions.

- ➔ Internet: [vtsa](#)
- ➔ Internet: [vtsa-f](#)

### General data

- Solutions with integrated inputs
- Width 18, 26 (VTSA and VTSA-F) and 42, 52 mm (VTSA only)
- With or without 24 V DC auxiliary power supply for solenoid coils (EMERGENCY-STOP circuitry) in the case of the 4I/40 version. The auxiliary power supply is always integrated in the version with 8 inputs and cannot be subsequently switched off using the DIL switch
- Selectable bus connection technology
  - Flat cable for AS-interface with 4I/40 version
  - 4-pin M12 round plug<sup>1)</sup> with 4I/40 and 8I/80 version
- Selectable addressing
  - Via bus connection (M12 or flat cable)

### Versions

- 1 to 8 valves, freely configurable
- With 4 or 8 inputs
- M12, M8, quick connection, tension spring or Sub-D connection technology
- Separating seals for the creation of pressure zones
- Suitable for vacuum
- Subsequent extensions either
  - via vacant positions
  - by converting the valve terminal

### Application

- Flexible and cost-effective connection of 1 or 8 valves (max. 8 solenoid coils) with input feedback
- Decentralised machine and system structures, for example
  - in handling technology
  - in conveyor technology
  - in the packaging industry
  - in sorting systems
  - suitable for energy chains thanks to connection via round cables

1) Suitable cable distributor from flat cable to M12 ➔ 59

# AS-interface® components



VTSA/VTSA-F valve terminal – Connection technology and addressing

| Types of valve terminal with AS-interface |        |                |        |                                            |    |            |    |                  |                  |
|-------------------------------------------|--------|----------------|--------|--------------------------------------------|----|------------|----|------------------|------------------|
| Type                                      | Valves | Solenoid coils | Inputs | Auxiliary power supply can be disconnected |    | Width (mm) |    |                  |                  |
|                                           |        |                |        | Yes                                        | No | 18         | 26 | 42 <sup>1)</sup> | 52 <sup>1)</sup> |
| VTSA/VTSA-F-ASI-4E4A-Z                    | 4      | 4              | 4      | ■                                          | –  | ■          | ■  | ■                | ■                |
| VTSA/VTSA-F-ASI-8E8A-Z                    | 8      | 8              | 8      | –                                          | ■  | ■          | ■  | ■                | ■                |

1) Width 42 and 52 mm not in the case of VTSA-F

| Permissible combinations in valve position allocation (examples) |         |     |     |     |
|------------------------------------------------------------------|---------|-----|-----|-----|
| Type                                                             | Slave n |     |     |     |
|                                                                  | 0       | 1   | 2   | 3   |
| 4l/4O VTSA/VTSA-F – 18 and 26 mm (2 valves per sub-base)         | M       | M   | M   | M   |
|                                                                  | M       | M   | M   | L   |
|                                                                  | M       | M   | –   | –   |
|                                                                  | M       | L   | –   | –   |
|                                                                  | ...     | ... | ... | ... |
|                                                                  | J       | M   | –   | –   |
|                                                                  | M       | J   | –   | –   |
|                                                                  | J       | J   | –   | –   |
| Special case                                                     | M       | M   | J   | L   |
|                                                                  |         |     |     |     |
| 4l/4O VTSA – 42 mm (1 valve per sub-base)                        | M       | M   | M   | M   |
|                                                                  | M       | M   | M   | L   |
|                                                                  | M       | M   | –   | –   |
|                                                                  | M       | –   | –   | –   |
|                                                                  | ...     | ... | ... | ... |
|                                                                  | J       | M   | –   | –   |
|                                                                  | J       | M   | M   | –   |
|                                                                  | ...     | ... | ... | ... |
|                                                                  | M       | J   | M   | –   |
|                                                                  | J       | J   | –   | –   |

| Permissible combinations in valve position allocation (examples) |                        |     |     |     |     |     |     |     |
|------------------------------------------------------------------|------------------------|-----|-----|-----|-----|-----|-----|-----|
| Type                                                             | Slave n plus slave n+1 |     |     |     |     |     |     |     |
|                                                                  | 0                      | 1   | 2   | 3   | 4   | 5   | 6   | 7   |
| 8E8A VTSA/VTSA-F                                                 | M                      | M   | M   | M   | M   | M   | M   | M   |
|                                                                  | M                      | M   | M   | L   | M   | M   | M   | L   |
|                                                                  | ...                    | ... | ... | ... | ... | ... | ... | ... |
|                                                                  | J                      | J   | J   | J   | –   | –   | –   | –   |
|                                                                  | J                      | J   | J   | M   | –   | –   | –   | –   |
|                                                                  | J                      | J   | M   | M   | –   | –   | –   | –   |
|                                                                  | ...                    | ... | ... | ... | ... | ... | ... | ... |
|                                                                  | J                      | J   | M   | M   | M   | M   | –   | –   |
|                                                                  | ...                    | ... | ... | ... | ... | ... | ... | ... |

1) - All valve slices can be freely configured (up to the maximum number of valve solenoids supported (4 or 8).

- A blanking plate can be used instead of the valve slice as a vacant position for one or two solenoid coils.

M Valve slice with single solenoid valve or a different valve slice with an output.

J Valve slice with double solenoid valve or a different valve slice with two outputs.

L Vacant position


# AS-interface® components

VTSA/VTSA-F valve terminal – Connection technology and addressing


FESTO

## Installation: Selectable connection technology for AS-interface


### Support for flat cables



- Straightforward cabling with flat cables in protected areas
- Fast system of installation with standard AS-interface cables
- Standard installation at the AS-interface with yellow flat cables is possible with the 4I/4O VTSA/VTSA-F version




### Support for round cables



Local round cable wiring system for areas subjected to consistently high stress:


- Permanently high humidity
- Need for flexible cabling using one cable
- Use in energy chains with highly flexible cables



- 1 Pre-assembled M12 round cable, 1 m, polyurethane
- 2 Selectable cable for additional slave, for example highly flexible cable for energy chains or PVC cable for applications requiring resistance to detergents


## Addressing

### Addressing device



- The addressing device to SPEC V2.1 can be used to scan the AS-interface from any point in the network. At all connected stations
- slave addresses can be read/changed
  - ID and IO codes can be read out
  - parameters can be read/changed
  - input/output data can be read and written (setting outputs)
  - error messages can be read out and quickly recognised

### AS-interface connections




- 1 M12 plug for AS-interface and incoming auxiliary supply
- 2 M12 socket for AS-interface and outgoing auxiliary supply

# AS-interface® components

VTSA/VTSA-F valve terminal – Connection technology and addressing

FESTO

## AS-interface flat cable distributor to round cable 2x M12



### Alternative connection concepts

- AS-interface connection technology for yellow and optionally for black flat cables
- Passive conversion of the signals to M12 socket and round cable via M12 socket
- Pre-assembled round cable, PUR, 1 m long
- Selectable PVC extension cable, 2.5 and 5 m, via additional M12 socket

### Selecting the cable

Optimised connection technologies at the AS-interface can be easily realised by selecting the right cable.


- Flat cables for all standard applications with installation-saving insulation displacement technology
- Round cables for applications with differing requirements, for example:
  - Energy chains with small radii and further requirements for highly flexible cables

- Applications with consistently high humidity
- Applications involving frequent cleaning and requiring cables resistant to detergents (PUR, PVC or other cables)
- Cabling systems using standard components (M12) preferred

### Easy to mount

- Direct mounting on a wall or machine frame

## Supplementary compact I/O modules



The valve terminals VTSA/VTSA-F can be supplemented with the compact I/O modules. The following are available:

- 8 inputs M8
- 4 inputs/3 outputs M12

# AS-interface® components

Key features – Display and operation

FESTO

## Display and operation

Each solenoid coil is allocated an LED which indicates its switching status.

- Indicator 12 shows the switching status of the pilot control for output 2
- Indicator 14 shows the switching status of the pilot control for output 4

### Manual override

The manual override enables the valve to be actuated when not electrically activated or energised.


The valve is activated by pushing the manual override. The set switching status can also be locked by turning the manual override.

Alternatives:


- A cover (code N or as accessory) can be fitted over the manual override to prevent it from being locked. The valve can only be actuated by pressing it.

- A cover (code V) can be fitted over the manual override to prevent it from being accidentally activated.

## Pneumatic connection and control elements



## Electrical connection and display components



# AS-interface® components

VTSA/VTSA-F valve terminal

FESTO

| Technical data                                            |                                                        |                                                                                 |                             |                             |
|-----------------------------------------------------------|--------------------------------------------------------|---------------------------------------------------------------------------------|-----------------------------|-----------------------------|
| Type                                                      |                                                        | VTSA/VTSA-F-ASI-4E4A-Z                                                          |                             | VTSA/VTSA-F-ASI-8E8A-Z      |
| Part No.                                                  |                                                        | Order via order code/valve terminal configurator                                |                             |                             |
| Assembly position                                         |                                                        | Any                                                                             |                             |                             |
| Digital inputs                                            | No. of digital inputs                                  | 4                                                                               | 8                           |                             |
|                                                           | Connection technology                                  | 5-pin M12, 3-pin M8, quick connection, tension spring, Sub-D                    |                             |                             |
|                                                           | Sensor supply via AS-interface                         | Short circuit and overload proof                                                |                             |                             |
|                                                           | Sensor connection                                      | 2-wire and 3-wire sensors                                                       |                             |                             |
|                                                           | Type                                                   | IEC 1131-2, type 02                                                             |                             |                             |
|                                                           | Input circuitry                                        | PNP (positive switching)                                                        |                             |                             |
| Valves                                                    | Number of solenoid coils                               | 4                                                                               | 8                           |                             |
|                                                           | Valve width [mm]                                       | 18/26/42/52 (width 42 and 52 mm only in the case of VTSA)                       |                             |                             |
|                                                           | External power supply 24 V DC (auxiliary power supply) | Set using DIL switch                                                            |                             | Yes                         |
| Max. current consumption of valves per solenoid coil [mA] |                                                        | 90                                                                              |                             |                             |
| AS-interface connection                                   | Connection technology                                  | Plug M12x1, 4-pin; socket M12x1, 4-pin <sup>2)</sup>                            |                             |                             |
|                                                           | Voltage range [V DC]                                   | 26.5 ... 31.6, reverse polarity protected                                       |                             |                             |
|                                                           | Residual ripple [mVss]                                 | 20                                                                              |                             |                             |
|                                                           | Electrical isolation fieldbus interface                | Optocoupler                                                                     |                             |                             |
|                                                           | Current consumption of inputs [mA]                     | Without auxiliary power supply                                                  | With auxiliary power supply | With auxiliary power supply |
|                                                           | Basic electronic load                                  | ≤25                                                                             | ≤25                         | ≤25                         |
|                                                           | Total input current                                    | 350                                                                             | 350                         | 350                         |
|                                                           | Total current consumption                              | Max. 500                                                                        | Max. 700                    | Max. 700                    |
| Load voltage connection                                   | Connection technology                                  | M12 connection <sup>2)</sup>                                                    |                             |                             |
|                                                           | Voltage range [V DC]                                   | 21.6 ... 26.4                                                                   |                             |                             |
|                                                           | Residual ripple [Vss]                                  | 4                                                                               |                             |                             |
| LED displays                                              | ASI-LED                                                | Green                                                                           |                             |                             |
|                                                           | AUX-PWR-LED                                            | Green                                                                           |                             |                             |
|                                                           | FAULT-LED                                              | Red                                                                             |                             |                             |
|                                                           | Inputs                                                 | Green                                                                           |                             |                             |
|                                                           | Valves                                                 | Yellow                                                                          |                             |                             |
| AS-interface data                                         | AS-interface specification                             | AS-interface Complete Spec 3.0                                                  |                             |                             |
|                                                           | Addressing range Slave                                 | 0, 1 ... 31                                                                     |                             |                             |
|                                                           | ID code                                                | ID = F <sub>H</sub> ; ID1 = F <sub>H</sub> <sup>1)</sup> ; ID2 = E <sub>H</sub> |                             |                             |
|                                                           | IO code                                                | 7 <sub>H</sub>                                                                  |                             |                             |
|                                                           | Profile                                                | S-7.FE                                                                          |                             |                             |

1) Factory setting, set to 0<sub>H</sub> by some programming devices (Spec. V2.1) when addressing the slave

2) Suitable cable distributor from flat cable to M12 → 59

| Operating and environmental conditions  |         |                                                   |
|-----------------------------------------|---------|---------------------------------------------------|
| Protection class (to EN 60529)          |         | IP65, NEMA 4 (in assembled state)                 |
| Electromagnetic compatibility           |         | Tested to 50295                                   |
| CE mark (see declaration of conformity) |         | To EU EMC Directive                               |
|                                         |         | To EU Low Voltage Directive                       |
| Certification                           |         | c UL us - Recognized (OL)                         |
|                                         |         | C-Tick                                            |
| Ambient temperature                     | [°C]    | −5 ... +50                                        |
| Storage temperature                     | [°C]    | −20 ... +40                                       |
| Materials                               | Housing | Die-cast aluminium, PA                            |
|                                         | Seals   | NBR, PUR                                          |
| Note on materials                       |         | RoHS-compliant                                    |
| Weight                                  | [g]     | AS-interface connection: 300, multi-pin node: 850 |

# AS-interface® components

VTSA/VTSA-F valve terminal – Connection blocks

FESTO



Note

The valve terminal VTSA with AS-interface connection is based on the same electrical manifold module as the valve terminal with multi-pin plug connection. This means it is possible to convert a valve terminal with







multi-pin plug connection using an AS-interface module. The technical specifications of the AS-interface system must be observed in this case.







→ Internet: vtisa

## Combinations of connection blocks and electronics modules for inputs

| Connection blocks     | Part No. | VTSA/VTSA-F-ASI-8E8A-Z | VTSA/VTSA-F-ASI-4E4A-Z |
|-----------------------|----------|------------------------|------------------------|
| CPX-AB-4-M12x2-5POL   | 195704   | ■                      | ■                      |
| CPX-AB-4-M12x2-5POL-R | 541254   | ■                      | ■                      |
| CPX-AB-8-KL-4POL      | 195708   | ■                      | ■                      |
| CPX-AB-1-Sub-BU-25POL | 525676   | ■                      | ■                      |
| CPX-AB-4-HAR-4POL     | 525636   | ■                      | ■                      |
| CPX-AB-8-M8-3POL      | 195706   | ■                      | ■                      |

## Pin allocation

| Connection block inputs                                                             |                                                                                                  | VTSA/VTSA-F-ASI-8E8A-Z                                                                           |                                                                                                                 | VTSA/VTSA-F-ASI-4E4A-Z                                                                                          |                                                                                                               |                                                                                                                 |
|-------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------|
| CPX-AB-4-M12X2-5POL                                                                 |                                                                                                  |                                                                                                  |                                                                                                                 |                                                                                                                 |                                                                                                               |                                                                                                                 |
|  | <br><b>X1</b> | <br><b>X3</b> | X1.1: 24 V <sub>SEN</sub><br>X1.2: Input x+1<br>X1.3: 0 V <sub>SEN</sub><br>X1.4: Input x<br>X1.5: FE (earth)   | X3.1: 24 V <sub>SEN</sub><br>X3.2: Input x+5<br>X3.3: 0 V <sub>SEN</sub><br>X3.4: Input x+4<br>X3.5: FE (earth) | X1.1: 24 V <sub>SEN</sub><br>X1.2: Input x+1<br>X1.3: 0 V <sub>SEN</sub><br>X1.4: Input x<br>X1.5: FE (earth) | X3.1: 24 V <sub>SEN</sub><br>X3.2: Input x+3<br>X3.3: 0 V <sub>SEN</sub><br>X3.4: Input x+2<br>X3.5: FE (earth) |
|                                                                                     | <br><b>X2</b> | <br><b>X4</b> | X2.1: 24 V <sub>SEN</sub><br>X2.2: Input x+3<br>X2.3: 0 V <sub>SEN</sub><br>X2.4: Input x+2<br>X2.5: FE (earth) | X4.1: 24 V <sub>SEN</sub><br>X4.2: Input x+7<br>X4.3: 0 V <sub>SEN</sub><br>X4.4: Input x+6<br>X4.5: FE (earth) | X2.1: 24 V <sub>SEN</sub><br>X2.2: n.c.<br>X2.3: 0 V <sub>SEN</sub><br>X2.4: Input x+1<br>X2.5: FE (earth)    | X4.1: 24 V <sub>SEN</sub><br>X4.2: n.c.<br>X4.3: 0 V <sub>SEN</sub><br>X4.4: Input x+3<br>X4.5: FE (earth)      |
| CPX-AB-8-M8-3POL                                                                    |                                                                                                  |                                                                                                  |                                                                                                                 |                                                                                                                 |                                                                                                               |                                                                                                                 |
|  | <br><b>X1</b> | <br><b>X5</b> | X1.1: 24 V <sub>SEN</sub><br>X1.3: 0 V <sub>SEN</sub><br>X1.4: Input x                                          | X5.1: 24 V <sub>SEN</sub><br>X5.3: 0 V <sub>SEN</sub><br>X5.4: Input x+4                                        | X1.1: 24 V <sub>SEN</sub><br>X1.3: 0 V <sub>SEN</sub><br>X1.4: Input x                                        | X5.1: 24 V <sub>SEN</sub><br>X5.3: 0 V <sub>SEN</sub><br>X5.4: Input x+2                                        |
|                                                                                     | <br><b>X2</b> | <br><b>X6</b> | X2.1: 24 V <sub>SEN</sub><br>X2.3: 0 V <sub>SEN</sub><br>X2.4: Input x+1                                        | X6.1: 24 V <sub>SEN</sub><br>X6.3: 0 V <sub>SEN</sub><br>X6.4: Input x+5                                        | X2.1: 24 V <sub>SEN</sub><br>X2.3: 0 V <sub>SEN</sub><br>X2.4: Input x+1                                      | X6.1: 24 V <sub>SEN</sub><br>X6.3: 0 V <sub>SEN</sub><br>X6.4: Input x+3                                        |
|                                                                                     | <br><b>X3</b> | <br><b>X7</b> | X3.1: 24 V <sub>SEN</sub><br>X3.3: 0 V <sub>SEN</sub><br>X3.4: Input x+2                                        | X7.1: 24 V <sub>SEN</sub><br>X7.3: 0 V <sub>SEN</sub><br>X7.4: Input x+6                                        | X3.1: 24 V <sub>SEN</sub><br>X3.3: 0 V <sub>SEN</sub><br>X3.4: Input x+1                                      | X7.1: 24 V <sub>SEN</sub><br>X7.3: 0 V <sub>SEN</sub><br>X7.4: Input x+3                                        |
|                                                                                     | <br><b>X4</b> | <br><b>X8</b> | X4.1: 24 V <sub>SEN</sub><br>X4.3: 0 V <sub>SEN</sub><br>X4.4: Input x+3                                        | X8.1: 24 V <sub>SEN</sub><br>X8.3: 0 V <sub>SEN</sub><br>X8.4: Input x+7                                        | X4.1: 24 V <sub>SEN</sub><br>X4.3: 0 V <sub>SEN</sub><br>X4.4: n.c.                                           | X8.1: 24 V <sub>SEN</sub><br>X8.3: 0 V <sub>SEN</sub><br>X8.4: n.c.                                             |

| Pin allocation                                                                      |                                                                                     |                                                                                                                                                                                                                                                                                             |                                                                                                                                                                                                                                                                                            |                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                                                       |
|-------------------------------------------------------------------------------------|-------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Connection block inputs                                                             |                                                                                     | VTSA/VTSA-F-ASI-8E8A-Z                                                                                                                                                                                                                                                                      |                                                                                                                                                                                                                                                                                            | VTSA/VTSA-F-ASI-4E4A-Z                                                                                                                                                                                                                                                                 |                                                                                                                                                                                                                                                                                       |
| CPX-AB-8-KL-4POL                                                                    |                                                                                     |                                                                                                                                                                                                                                                                                             |                                                                                                                                                                                                                                                                                            |                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                                                       |
|    |    | X1.0: 24 V <sub>SEN</sub><br>X1.1: 0 V <sub>SEN</sub><br>X1.2: Input x<br>X1.3: FE (earth)                                                                                                                                                                                                  | X5.0: 24 V <sub>SEN</sub><br>X5.1: 0 V <sub>SEN</sub><br>X5.2: Input x+4<br>X5.3: FE (earth)                                                                                                                                                                                               | X1.0: 24 V <sub>SEN</sub><br>X1.1: 0 V <sub>SEN</sub><br>X1.2: Input x<br>X1.3: FE (earth)                                                                                                                                                                                             | X5.0: 24 V <sub>SEN</sub><br>X5.1: 0 V <sub>SEN</sub><br>X5.2: Input x+2<br>X5.3: FE (earth)                                                                                                                                                                                          |
|                                                                                     |                                                                                     | X2.0: 24 V <sub>SEN</sub><br>X2.1: 0 V <sub>SEN</sub><br>X2.2: Input x+1<br>X2.3: FE (earth)                                                                                                                                                                                                | X6.0: 24 V <sub>SEN</sub><br>X6.1: 0 V <sub>SEN</sub><br>X6.2: Input x+5<br>X6.3: FE (earth)                                                                                                                                                                                               | X2.0: 24 V <sub>SEN</sub><br>X2.1: 0 V <sub>SEN</sub><br>X2.2: Input x+1<br>X2.3: FE (earth)                                                                                                                                                                                           | X6.0: 24 V <sub>SEN</sub><br>X6.1: 0 V <sub>SEN</sub><br>X6.2: Input x+3<br>X6.3: FE (earth)                                                                                                                                                                                          |
|                                                                                     |                                                                                     | X3.0: 24 V <sub>SEN</sub><br>X3.1: 0 V <sub>SEN</sub><br>X3.2: Input x+2<br>X3.3: FE (earth)                                                                                                                                                                                                | X7.0: 24 V <sub>SEN</sub><br>X7.1: 0 V <sub>SEN</sub><br>X7.2: Input x+6<br>X7.3: FE (earth)                                                                                                                                                                                               | X3.0: 24 V <sub>SEN</sub><br>X3.1: 0 V <sub>SEN</sub><br>X3.2: Input x+1<br>X3.3: FE (earth)                                                                                                                                                                                           | X7.0: 24 V <sub>SEN</sub><br>X7.1: 0 V <sub>SEN</sub><br>X7.2: Input x+3<br>X7.3: FE (earth)                                                                                                                                                                                          |
|                                                                                     |                                                                                     | X4.0: 24 V <sub>SEN</sub><br>X4.1: 0 V <sub>SEN</sub><br>X4.2: Input x+3<br>X4.3: FE (earth)                                                                                                                                                                                                | X8.0: 24 V <sub>SEN</sub><br>X8.1: 0 V <sub>SEN</sub><br>X8.2: Input x+7<br>X8.3: FE (earth)                                                                                                                                                                                               | X4.0: 24 V <sub>SEN</sub><br>X4.1: 0 V <sub>SEN</sub><br>X4.2: n.c.<br>X4.3: FE (earth)                                                                                                                                                                                                | X8.0: 24 V <sub>SEN</sub><br>X8.1: 0 V <sub>SEN</sub><br>X8.2: n.c.<br>X8.3: FE (earth)                                                                                                                                                                                               |
| CPX-AB-1-SUB-BU-25POL                                                               |                                                                                     |                                                                                                                                                                                                                                                                                             |                                                                                                                                                                                                                                                                                            |                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                                                       |
|  |  | 1: Input x<br>2: Input x+1<br>3: Input x+2<br>4: Input x+3<br>5: 24 V <sub>SEN</sub><br>6: 0 V <sub>SEN</sub><br>7: 24 V <sub>SEN</sub><br>8: 0 V <sub>SEN</sub><br>9: 24 V <sub>SEN</sub><br>10: 24 V <sub>SEN</sub><br>11: 0 V <sub>SEN</sub><br>12: 0 V <sub>SEN</sub><br>13: FE (earth) | 14: Input x+4<br>15: Input x+5<br>16: Input x+6<br>17: Input x+7<br>18: 24 V <sub>SEN</sub><br>19: 24 V <sub>SEN</sub><br>20: 24 V <sub>SEN</sub><br>21: 24 V <sub>SEN</sub><br>22: 0 V <sub>SEN</sub><br>23: 0 V <sub>SEN</sub><br>24: 0 V <sub>SEN</sub><br>25: FE (earth)<br>Socket: FE | 1: Input x<br>2: Input x+1<br>3: Input x+1<br>4: n.c.<br>5: 24 V <sub>SEN</sub><br>6: 0 V <sub>SEN</sub><br>7: 24 V <sub>SEN</sub><br>8: 0 V <sub>SEN</sub><br>9: 24 V <sub>SEN</sub><br>10: 24 V <sub>SEN</sub><br>11: 0 V <sub>SEN</sub><br>12: 0 V <sub>SEN</sub><br>13: FE (earth) | 14: Input x+2<br>15: Input x+3<br>16: Input x+3<br>17: n.c.<br>18: 24 V <sub>SEN</sub><br>19: 24 V <sub>SEN</sub><br>20: 24 V <sub>SEN</sub><br>21: 24 V <sub>SEN</sub><br>22: 0 V <sub>SEN</sub><br>23: 0 V <sub>SEN</sub><br>24: 0 V <sub>SEN</sub><br>25: FE (earth)<br>Socket: FE |
|                                                                                     |                                                                                     |                                                                                                                                                                                                                                                                                             |                                                                                                                                                                                                                                                                                            |                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                                                       |
| CPX-AB-4-HAR-4POL                                                                   |                                                                                     |                                                                                                                                                                                                                                                                                             |                                                                                                                                                                                                                                                                                            |                                                                                                                                                                                                                                                                                        |                                                                                                                                                                                                                                                                                       |
|  |  | X1.1: 24 V <sub>SEN</sub><br>X1.2: Input x+1<br>X1.3: 0 V <sub>SEN</sub><br>X1.4: Input x                                                                                                                                                                                                   | X3.1: 24 V <sub>SEN</sub><br>X3.2: Input x+5<br>X3.3: 0 V <sub>SEN</sub><br>X3.4: Input x+4                                                                                                                                                                                                | X1.1: 24 V <sub>SEN</sub><br>X1.2: Input x+1<br>X1.3: 0 V <sub>SEN</sub><br>X1.4: Input x                                                                                                                                                                                              | X3.1: 24 V <sub>SEN</sub><br>X3.2: Input x+3<br>X3.3: 0 V <sub>SEN</sub><br>X3.4: Input x+2                                                                                                                                                                                           |
|                                                                                     |                                                                                     | X2.1: 24 V <sub>SEN</sub><br>X2.2: Input x+3<br>X2.3: 0 V <sub>SEN</sub><br>X2.4: Input x+2                                                                                                                                                                                                 | X4.1: 24 V <sub>SEN</sub><br>X4.2: Input x+7<br>X4.3: 0 V <sub>SEN</sub><br>X4.4: Input x+6                                                                                                                                                                                                | X2.1: 24 V <sub>SEN</sub><br>X2.2: n.c.<br>X2.3: 0 V <sub>SEN</sub><br>X2.4: Input x+1                                                                                                                                                                                                 | X4.1: 24 V <sub>SEN</sub><br>X4.2: n.c.<br>X4.3: 0 V <sub>SEN</sub><br>X4.4: Input x+3                                                                                                                                                                                                |


# AS-interface® components

VTSA/VTSA-F valve terminal – Dimensions

FESTO

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



- 1 Solenoid valve 18 mm
- 2 Solenoid valve 26 mm
- 3 Solenoid valve 42 mm  
(not in the case of VTSA-F)
- 4 Solenoid valve 52 mm  
(not in the case of VTSA-F)
- 5 Threaded connection G $\frac{1}{2}$  or  
 $\frac{1}{2}$ NPT
- 6 Threaded connection G $\frac{3}{8}$  or  
 $\frac{3}{8}$ NPT

- 7 Threaded connection G $\frac{1}{4}$  or  
 $\frac{1}{4}$ NPT
- 8 Threaded connection G $\frac{1}{8}$  or  
 $\frac{1}{8}$ NPT
- 9 H-rail
- 10 H-rail mounting
- 11 Mounting hole

- 12 Additional mounting bracket
- 13 Inscription label
- 14 End plate
- 15 Plug M12
- 16 Additional mounting bracket
- 17 Cover cap/manual override

- n02 Number of manifold blocks  
38 mm
- n01 Number of manifold blocks  
54 mm
- n1 Number of manifold blocks  
43 mm
- n2 Number of manifold blocks  
59 mm
- nzwp Number of supply plates

| Width                                    | L1                                                                                           |
|------------------------------------------|----------------------------------------------------------------------------------------------|
| 18 mm                                    | $71.3 + n02 \times 38 + nzwp \times 38 + 37.3$                                               |
| 26 mm                                    | $71.3 + n01 \times 54 + nzwp \times 38 + 37.3$                                               |
| 42 mm                                    | $71.3 + n1 \times 43 + nzwp \times 38 + 37.3$                                                |
| 52 mm                                    | $71.3 + n2 \times 59 + nzwp \times 38 + 37.3$                                                |
| Mixture of 18 mm, 26 mm, 42 mm and 52 mm | $71.3 + n02 \times 38 + n01 \times 54 + n1 \times 43 + n2 \times 59 + nzwp \times 38 + 37.3$ |


# AS-interface® components

VTSA/VTSA-F valve terminal with soft-start valve

FESTO

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)













| Width                                    | L1                                                                                           |
|------------------------------------------|----------------------------------------------------------------------------------------------|
| 18 mm                                    | $71.3 + n02 \times 38 + nzwp \times 38 + 37.3$                                               |
| 26 mm                                    | $71.3 + n01 \times 54 + nzwp \times 38 + 37.3$                                               |
| 42 mm                                    | $71.3 + n1 \times 43 + nzwp \times 38 + 37.3$                                                |
| 52 mm                                    | $71.3 + n2 \times 59 + nzwp \times 38 + 37.3$                                                |
| Mixture of 18 mm, 26 mm, 42 mm and 52 mm | $71.3 + n02 \times 38 + n01 \times 54 + n1 \times 43 + n2 \times 59 + nzwp \times 38 + 37.3$ |

# AS-interface® components

VTSA/VTSA-F valve terminal – Accessories

**FESTO**







| Ordering data                                                                       |                                                                                  |                             |          |                   |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------|-----------------------------|----------|-------------------|
|                                                                                     | Description                                                                      |                             | Part No. | Type              |
| Bus connection                                                                      |                                                                                  |                             |          |                   |
|    | AS-interface flat cable, yellow                                                  | 100 m                       | 18940    | KASI-1,5-Y-100    |
|                                                                                     | AS-interface flat cable, black                                                   | 100 m                       | 18941    | KASI-1,5-Z-100    |
|    | Flat cable blanking plug                                                         |                             | 196090   | ASI-SD-FK-BL      |
|    | AS-interface flat cable distributor                                              | Parallel cable              | 18786    | ASI-KVT-FK        |
|    | AS-interface flat cable distributor                                              | Symmetrical cable           | 18797    | ASI-KVT-FK-S      |
|    | Cable cap for flat cable (scope of delivery 50 pieces)                           |                             | 18787    | ASI-KK-FK         |
|   | Cable sleeve (scope of delivery 20 pieces)                                       |                             | 165593   | ASI-KT-FK         |
|  | Socket M12, 4-pin                                                                | For AS-interface flat cable | 18789    | ASI-SD-PG-M12     |
|  | Socket M12, 5-pin                                                                | For round cable             | 18324    | FBSD-GD-9-5POL    |
| Cable distributor                                                                   |                                                                                  |                             |          |                   |
|  | AS-Interface data to socket M12, 4-pin                                           |                             | 572225   | NEFU-X22F-M12G4   |
|  | AS-Interface data and load voltage supply to socket M12, 4-pin                   |                             | 572226   | NEFU-X24F-M12G4   |
|  | AS-Interface data and load voltage supply to socket M12, 4-pin, cable length 1 m |                             | 572227   | NEFU-X24F-1-M12G4 |
| DUO plug                                                                            |                                                                                  |                             |          |                   |
|  | Plug M12 for 2 sensor cables                                                     | 4-pin, PG11                 | 18779    | SEA-GS-11-DUO     |
|                                                                                     |                                                                                  | 5-pin, PG11                 | 192010   | SEA-5GS-11-DUO    |

| Ordering data                                                                       |                                                                    |                               |          |                            |
|-------------------------------------------------------------------------------------|--------------------------------------------------------------------|-------------------------------|----------|----------------------------|
|                                                                                     | Description                                                        |                               | Part No. | Type                       |
| Sensor plugs                                                                        |                                                                    |                               |          |                            |
|    | Straight sensor plug                                               | M12, 4-pin, PG7               | 18666    | SEA-GS-7                   |
|    | Straight sensor plug                                               | M12, 5-pin, PG7               | 175487   | SEA-M12-5GS-PG7            |
|    | Straight sensor plug                                               | M12, PG9 connector            | 18778    | SEA-GS-9                   |
|    | Straight sensor plug for cable Ø 2.5 mm                            | M12, 4-pin                    | 192008   | SEA-4GS-7-2,5              |
|                                                                                     | Straight sensor plug                                               | M8, screw-in, 3-pin           | 192009   | SEA-3GS-M8-S               |
|    | Straight sensor plug                                               | M8, solderable, 3-pin         | 18696    | SEA-GS-M8                  |
|    | Harax sensor plug                                                  | 4-pin                         | 525928   | SEA-GS-HAR-4POL            |
|   | Sub-D plug                                                         | 25-pin                        | 527522   | SD-SUB-D-ST25              |
|  | Cover cap (scope of delivery 10 pieces)                            | M12                           | 165592   | ISK-M12                    |
|                                                                                     |                                                                    | M8                            | 177672   | ISK-M8                     |
| Connecting cable                                                                    |                                                                    |                               |          |                            |
|  | Modular system for connecting cables<br>➔ Internet: nebu           |                               | –        | NEBU-...                   |
|                                                                                     | Straight plug M8, 3-pin, straight socket<br>M8, 3-pin              | 0.5 m                         | 541346   | NEBU-M8G3-K-0.5-M8G3       |
|                                                                                     |                                                                    | 1.0 m                         | 541347   | NEBU-M8G3-K-1-M8G3         |
|                                                                                     |                                                                    | 2.5 m                         | 541348   | NEBU-M8G3-K-2.5-M8G3       |
|                                                                                     |                                                                    | 5.0 m                         | 541349   | NEBU-M8G3-K-5-M8G3         |
|                                                                                     | Straight plug M12, 4-pin, straight socket<br>M12, 5-pin            | 0.5 m                         | 8000208  | NEBU-M12G5-K-0.5-M12G4     |
| T-type plug connector                                                               |                                                                    |                               |          |                            |
|  | Plug M12, A-coded, 4-pin                                           | 2x socket M12, A-coded, 5-pin | 8005310  | NEDY-L2R1-V1-M12G5-N-M12G4 |
|                                                                                     |                                                                    | 2x socket M8, A-coded, 3-pin  | 8005311  | NEDY-L2R1-V1-M8G3-N-M12G4  |
|  | Modular system for sensor/actuator distributor<br>➔ Internet: nedy |                               | –        | NEDY-...                   |

# AS-interface® components

VTSA/VTSA-F valve terminal – Accessories


**FESTO**

| Ordering data                                                                       |                                                                     |         |          |                         |
|-------------------------------------------------------------------------------------|---------------------------------------------------------------------|---------|----------|-------------------------|
|                                                                                     | Description                                                         |         | Part No. | Type                    |
| Miscellaneous                                                                       |                                                                     |         |          |                         |
|    | Primary switched mode, modular power supply<br>24 V DC power supply | 5 A     | 2247681  | CACN-3A-1-5             |
|                                                                                     |                                                                     | 10 A    | 2247682  | CACN-3A-1-10            |
|    | Addressing device (power supply plug included in scope of delivery) |         | 18959    | ASI-PRG-ADR             |
|    | Addressing cable                                                    |         | 18960    | KASI-ADR                |
|    | AS-interface input module for 8 inputs M8                           |         | 542124   | ASI-8DI-M8-3POL         |
|    | AS-interface input/output module for 4 inputs/3 outputs M12         |         | 542125   | ASI-4DI3DO-M12X2-5POL-Z |
|   | Clip-on inscription label holder for valve cap (pack of 5)          |         | 540888   | ASCF-T-S6               |
|  | Inscription label holder for connection blocks (pack of 5)          |         | 540889   | ASCF-M-S6               |
|  | H-rail to EN 60715                                                  |         | 35430    | NRH-35-2000             |
|  | H-rail mounting                                                     |         | 526032   | CPX-CPA-BG-NRH          |
| User's manual                                                                       |                                                                     |         |          |                         |
|  | Description of the valve terminal VTSA/VTSA-F                       | German  | 538922   | P.BE-VTSA-44-DE         |
|                                                                                     |                                                                     | English | 538923   | P.BE-VTSA-44-EN         |
|                                                                                     |                                                                     | French  | 538925   | P.BE-VTSA-44-FR         |
|                                                                                     |                                                                     | Italian | 538926   | P.BE-VTSA-44-IT         |
|                                                                                     |                                                                     | Spanish | 538924   | P.BE-VTSA-44-ES         |

## AS-interface® components

Compact I/O modules and valve interfaces to Spec. V2.1

FESTO



### Compact I/O modules to Spec. V2.1

#### General description

- Highly compact modules
- Encapsulated, sturdy electronics
- Inputs/outputs to IEC1131, PNP
- Short circuit proof, overload proof
- Inputs suitable for proximity sensors, inductive, capacitive or optical sensors and light barriers
- Ideal for use in decentralised handling and assembly as well as universal applications with increased requirements
- AS-interface Specification V2.11
- A/B mode
- Bus and auxiliary power supply looped through via 2x M12
- Quick installation
- Individual module diagnostics

#### Module with 8 inputs

- Two slaves in one housing
- 8 inputs M8, 3-pin, 200 mA per input
- Peripherals faults per slave, two fault LEDs
- Status display per input
- Supply exclusively from "yellow" AS-interface cable, the pins for the auxiliary power supply are simply looped through
- This permits cascading of the input/output modules

#### Module with 4 inputs/3 outputs

- Individual slave
- 4 inputs M12, 5-pin, with double allocation, 200 mA per input
- 3 outputs M12, 5-pin, with double allocation, 1 A per output
- Peripherals fault, fault LED
- Status display for each input and output
- Inputs are supplied exclusively from the "yellow" AS-interface cable
- Outputs are supplied exclusively from the "black" AS-interface cable

# AS-interface® components

Compact I/O modules and valve interfaces

FESTO

## Applications



The M12 bus connection standardised in the AS-interface specification offers various advantages:

- Use of standardised, pre-assembled M12 connecting cables
- One cable instead of two
- Installation-saving, quick M12 screw-type lock
- Flexible selection and optimisation of the necessary cable qualities in areas with permanently high stress, for example for

- energy chains
- robot arms (torsion)
- environments with higher moisture content
- aggressive media


This connection technology makes compact modules ideal for use both in demanding and extremely tight conditions.

Decentralised machine and system structures, for example


- Handling technology
- Conveyor technology
- Packaging industry
- Sorting systems
- Upstream functions via energy chains and robot arms

## Tips on use


- In addition to valve terminals for optimising the number of inputs.




- Suitable for valve terminals with M12 bus connection for looping through the bus via M12



- Universal applications for all commonly used sensors and light barriers up to 200 mA per channel



- Universal outputs 1 A, up to 2 A (approx. 50 W) can be connected by means of parallel connection in the DUO plug




# AS-interface® components

Compact I/O modules and valve interfaces

FESTO

## AS-interface flat cable distributor to round cable 2x M12



### Alternative connection concepts

- AS-interface connection technology for yellow and optionally for black flat cables
- Passive conversion of the signals to M12 socket and round cable via M12 socket
- Pre-assembled round cable, PUR, 1 m long
- Alternatively PVC extension cable, or another suitable cable of any length, via additional M12 socket

### Selecting the cable

Optimised connection technologies at the AS-interface can be easily achieved by selecting the right cable.

- Flat cables for all standard applications with installation-saving insulation displacement technology
- Round cables for applications with differing requirements, for example:
  - Energy chains with small radii and further requirements for highly flexible cables

- Applications with consistently high humidity
- Applications involving frequent cleaning and requiring cables resistant to detergents (PUR, PVC or other cables)
- Cabling systems using standard components (M12) preferred

### Easy to fit

- Direct mounting on a wall or machine frame

## Tips on use and installation (inputs/outputs)


### Input module 8DI-M8

Connection technologies based on M8 take account of the increasing trend towards miniaturisation. Sensors with

pre-assembled M8 connecting cables or with M8 plugs can be directly connected in a 1:1 relationship. This

simplifies allocation and troubleshooting. Individual sensors or cables

can be easily and quickly replaced in the event of faults.



# AS-interface® components

Compact I/O modules and valve interfaces

FESTO

## Tips on use and installation (inputs/outputs)

### Input/output module 4DI3DO-M12

Sturdy M12 connection technology is still an accepted standard for inputs and outputs. Direct connection for sensors with M12 connection. The M12 interfaces with double allocation can be split into 2xM12 or 2xM8 via DUO plugs, DUO cables or T-adapters.


The standard for valves with central plug (EN 60947-5-2 and ISO 20401) defines double allocation for M12 or M8. This means that a double solenoid valve and a single solenoid valve can be directly connected to a

compact AS-interface module using a 1:1 connection. This simplifies allocation and troubleshooting. Individual valves or cables can be easily and quickly replaced in the event of faults.



Note

M8 4-pin adapter cables can be configured to M12 5-pin in Festo's modular system for connecting cables (NEBU...) so that even compact valve plugs as in MPA-S can be directly connected via pre-assembled cables.



# AS-interface® components

Compact I/O modules and valve interfaces

FESTO

## Tips on use and installation (AS-interface)

The compact I/O modules feature 4-pin M12 connections for bus IN and bus OUT. As per the AS-interface

specification, the two signal cables for the bus and the optional 24 V DC auxiliary power supply are accommodated


on this one connection. All 4 connections are looped through so that a number of modules and even

subsequent valve terminals can be cascaded.

### Input module 8DI-M8


Supply to the inputs is provided exclusively from the "yellow" AS-interface cable at this module, i.e. the pins for the auxiliary power supply are not used. This means that the following connection technologies can be realised in addition to the connections via M12 round plug connectors:

- Cable distributor NEFU-X2, directly assembled.
- This permits cost-effective and quick connection of a number of directly adjacent modules.
- A transition to valve terminals such as CPV is possible directly and without converters.



If there is an input module at the end of a string, the flat cable can also be routed through a specially sealed connector.

- Connection socket ASI-SD-PG-M12, directly assembled.
- Use at valve terminals with M12 is also possible, provided the auxiliary power supply is not required.




### Input/output module 4DI3DO-M12

Supply to the inputs is provided exclusively from the "yellow" AS-interface cable and supply to the outputs is provided exclusively from the "black" AS-interface cable at this module. Supply is provided either completely by an M12 installation or by means of a suitable converter such as the flat cable distributor NEFU-X24F-M12G4.

 Note

The contact load capacity of an M12 pin is limited to 4 A. With cascaded modules, ensure that the maximum current load of the first M12 connection in a series will not be exceeded even in a worst case scenario.




## Voltage drop on cables with M12 connection


Note that the voltage drop on an M12 cross sections. The cable lengths must be sized in accordance with the permissible voltage tolerances for the

AS-interface signal and the outputs for consuming devices with additional load voltage. The following graphs provide an initial orientation (non-linear scaling of the cable length):

Voltage drop U (V) for cable cross section 0.34 mm<sup>2</sup> with M12



Voltage drop U (V) for cable cross section 0.25 mm<sup>2</sup> with M12



# AS-interface® components

Compact I/O modules and valve interfaces

FESTO

## Installation



Installation for consuming devices with high current consumption

If several amperes are to be tapped per module, a suitable supply must be ensured via the corresponding

number of distributors (see the following example). This means that the

max. 3 A per module can be simultaneously switched. Note also that the

voltage drop increases with large currents in the flat cables ( $2 \times 1.5 \text{ mm}^2$ ).




## Alternative M12 installation with branch lines

Installation via branch lines can also be selected for straight M12 installation as an alternative to the

looped-through AS-i bus. The T-adapter FB-TA-M12-5POL is

ideal for this (bus IN: socket, bus OUT: plug).



# AS-interface® components

Compact I/O modules and valve interfaces

FESTO

## Assembly of the compact AS-interface modules

### Wall mounting

The AS-interface modules can be mounted on flat surfaces in almost any position using the existing mounting holes and two M4 screws.




#### Note

The modules are protected against short circuit using a thermal fuse. This can result in the housing heating up to over 100 °C with short circuits of long duration.


You should therefore install the modules on a base and in an environment designed for this temperature and which is free of fire risk due to ignition (ATEX category T4 – up to 135°).

### Wall mounting – Compact I/O modules




With the compact I/O modules, the mounting holes are covered by inscription labels.

### Mounting on profiles (ITEM, etc.)



With slot nuts for M4, otherwise see wall mounting.

### H-rail mounting



A mounting kit is available that can be used on an H-rail. On the compact CP modules, the mounting holes are covered by inscription labels.

The following mounting kit is required for H-rail mounting:

- CP-TS-HS35
- This enables mounting on H-rails to EN 60715.

# AS-interface® components

Compact I/O modules and valve interfaces

FESTO

## Function

Digital input modules facilitate the connection of proximity sensors or other digital 24 V DC sensors (inductive, capacitive, light barriers, etc.), PNP.

## Applications

- Input module for 24 V DC sensor signals
- Double slave, two slaves in one housing
- M8 plug connection technology, single allocation
- The input status of each input signal is indicated on an allocated green LED
- 24 V DC supply for all connected sensors provided via the ("yellow") AS-interface cable
- Peripherals fault LED for short circuit/undervoltage of sensor supply for each AS-interface slave
- Modules support A/B mode in accordance with Spec. V2.11
- Bus connection 2x M12 for bus in and bus out
- Bus and auxiliary power supply looped through for cascading with output modules



| General technical data |                                                                           |                                              |
|------------------------|---------------------------------------------------------------------------|----------------------------------------------|
| Type                   | ASI-8DI-M8-3POL                                                           |                                              |
| Digital inputs         | No. of inputs                                                             | 8                                            |
|                        | Power supply 24 V DC                                                      | From the AS-interface ("yellow" cable)       |
|                        | Intrinsic current consumption of electronics [mA]                         | Typically 35 (inputs not connected)          |
|                        | Input current at 24 V DC (from sensor) [mA]                               | Typically 6                                  |
|                        | Fuse protection for sensors and electronic module                         | Internal thermal short circuit protection    |
|                        | Max. current consumption per sensor [A]                                   | 0.24                                         |
|                        | Max. current consumption of sensor supply, residual current per slave [A] | 0.24                                         |
|                        | Nominal operating voltage for sensors [V]                                 | 24                                           |
|                        | Operating voltage range for sensors [V DC]                                | 18 ... 30                                    |
|                        | Protection against polarity reversal                                      | For logic and sensor supply and AS-interface |
|                        | Electrical separation                                                     |                                              |
|                        | • between the channels                                                    | None                                         |
|                        | • to the AS-interface system                                              | None                                         |
|                        | Logic level                                                               |                                              |
|                        | • Signal 0 [V]                                                            | ≤5                                           |
|                        | • Signal 1 [V]                                                            | ≥-11                                         |
|                        | Input delay [ms]                                                          | Typically 3                                  |
|                        | Switching logic                                                           | PNP                                          |
|                        | Input characteristic curve                                                | To IEC 1131-2                                |

# AS-interface® components

Compact I/O modules and valve interfaces

FESTO

| General technical data                          |                                                       |                                                                                                                                                |
|-------------------------------------------------|-------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------|
| Type                                            | ASI-8DI-M8-3POL                                       |                                                                                                                                                |
| General data                                    | Protection class to EN 60529                          | IP65/IP67 (when fully plugged in or fitted with protective cap)                                                                                |
|                                                 | Material                                              | Polybuteneterephthalate                                                                                                                        |
|                                                 | Dimensions (LxWxD) [mm]                               | 151 x 30 x 30                                                                                                                                  |
|                                                 | Weight [g]                                            | 190                                                                                                                                            |
| LED displays                                    | Inputs                                                | 8 green                                                                                                                                        |
|                                                 | AS-interface LED                                      | Power/green                                                                                                                                    |
|                                                 | FAULT-LED (fault 1, fault 2)                          | Fault LED/red per slave                                                                                                                        |
| AS-interface connection/load voltage connection | Connection with the AS-interface                      | Via M12 connecting cables, 4-wire                                                                                                              |
|                                                 | Watchdog function                                     | Active after 50 ms                                                                                                                             |
|                                                 | Peripherals fault/diagnostics                         | Short circuit/overload (thermal fuse on each channel) in accordance with specification c.S.2.1, two red fault LEDs<br>Automatic voltage return |
|                                                 | AS-interface bus voltage [V]                          | 26.5 ... 31.6                                                                                                                                  |
|                                                 | Total current consumption of AS-interface [mA]        | Max. 350                                                                                                                                       |
|                                                 | Current-carrying capacity of M12 pins (AS-i, AUX) [A] | Max. 4                                                                                                                                         |
|                                                 | AS-interface data                                     |                                                                                                                                                |
|                                                 | • IO code                                             | 0 <sub>h</sub>                                                                                                                                 |
|                                                 | • ID code 1                                           | A <sub>h</sub>                                                                                                                                 |
|                                                 | • ID code 2                                           | E <sub>h</sub>                                                                                                                                 |
|                                                 | • Profile                                             | S-0.A.E                                                                                                                                        |
|                                                 | AS-interface address (factory setting)                | #1A, #2A                                                                                                                                       |
|                                                 | AS-interface specification                            | 2.11 (compatible with 3.0)                                                                                                                     |

| Operating and environmental conditions       |                                                                                  |  |
|----------------------------------------------|----------------------------------------------------------------------------------|--|
| Type                                         | ASI-8DI-M8-3POL                                                                  |  |
| Protection class to DIN 60529                | IP65/IP67 (when fully plugged-in or fitted with protective cover)                |  |
| Ambient temperature [°C]                     | -5 ... +50                                                                       |  |
| Storage temperature [°C]                     | -20 ... +70                                                                      |  |
| Corrosion resistance class CRC <sup>1)</sup> | 1                                                                                |  |
| CE mark (see declaration of conformity)      | To EU EMC Directive <sup>2)</sup><br>To EU Explosion Protection Directive (ATEX) |  |
| Certification                                | c UL us - Listed (OL)                                                            |  |

- 1) Corrosion resistance class 1 as per Festo standard 940 070  
Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.
- 2) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: [www.festo.com/sp](http://www.festo.com/sp) → Certificates.  
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

| Certifications ATEX              |                             |  |
|----------------------------------|-----------------------------|--|
| ATEX category gas                | II 3G                       |  |
| Ex-ignition protection type gas  | Ex nA IIC T4 X Gc           |  |
| ATEX category dust               | II 3D                       |  |
| EX-ignition protection type dust | Ex tc IIIC T115°C X Dc IP67 |  |
| ATEX ambient temperature [°C]    | -5 ≤ Ta ≤ +50               |  |




## Note

For the operation of device combinations in hazardous areas, the lowest common zone, temperature class and ambient temperature of the individual devices determine the possible use of the entire module.

## Connection and display components

ASI-8DI-M8-3POL



- 1 AS-interface connection, incoming
- 2 Status LED (green)
- 3 Red LED for short circuit/overload display
- 4 Green LED for status display (one LED per input)
- 5 Sensor connections
- 6 AS-interface connection, outgoing

## Pin allocation for sensor connections ASI-8DI-M8-3POL

| Pin allocation | Pin | Signal  | Description               | Pin | Signal |
|----------------|-----|---------|---------------------------|-----|--------|
|                | 1   | 24 V DC | Operating voltage 24 V DC | 1   | 24 V   |
|                | 3   | 0 V     | Operating voltage 0 V     | 3   | 0 V    |
|                | 4   | Ix*     | Sensor signal             | 4   | Ix+1*  |

\* Ix = Input x

# AS-interface® components

Compact I/O modules and valve interfaces

FESTO

## Function

Combined digital input and output modules permit the connection of proximity sensors or other 24 V DC sensors (inductive, capacitive, etc.) as well as up to 3 consuming devices 24 V DC/1 A. The electrical outputs activate actuators such as individual valves, lamps, signal equipment and many more.



Note

Optimum actuation for valves with M12 central plug.

Plugs with double allocation are separated using a T-adapter, DUO plug or DUO cable.

## Applications

- Input/output module for 24 V DC sensor signals and actuators, PNP
- Single slave, contains an AS-interface chip
- M12 plug connection technology, 5-pin, double allocation
- Peripherals fault LED for short circuit/undervoltage of sensors or actuators

- Modules support A/B mode in accordance with Spec. V2.11
- Bus connection 2x M12 for bus in and bus out
- Bus and auxiliary power supply looped through for cascading with further output modules
- Inputs:
  - The input status of each input signal is indicated on an allocated green LED
  - 24 V DC supply for all connected sensors provided via the ("yellow") AS-interface cable
- Outputs:
  - The output status of each output signal is indicated on an allocated yellow LED
  - 24 V DC supply for all connected actuators is provided via the ("black") AS-interface cable



| General technical data |                                                                           |                                              |
|------------------------|---------------------------------------------------------------------------|----------------------------------------------|
| Type                   |                                                                           | ASI-4DI3DO-M12x2-5POL-Z                      |
| Digital inputs         | No. of inputs                                                             | 4                                            |
|                        | Power supply 24 V DC                                                      | From the AS-interface ("yellow" cable)       |
|                        | Intrinsic current consumption of electronics [mA]                         | Typically 35 (inputs not connected)          |
|                        | Input current at 24 V DC (from sensor) [mA]                               | Typically 6                                  |
|                        | Fuse protection for sensors                                               | Internal thermal short circuit protection    |
|                        | Max. current consumption per sensor [A]                                   | 0.24                                         |
|                        | Max. current consumption of sensor supply, residual current per slave [A] | 0.25                                         |
|                        | Nominal operating voltage for sensors [V]                                 | 24                                           |
|                        | Operating voltage range for sensors [V DC]                                | 18 ... 30                                    |
|                        | Protection against polarity reversal                                      | For logic and sensor supply and AS-interface |
|                        | Electrical separation                                                     |                                              |
|                        | • between the channels                                                    | None                                         |
|                        | • to the AS-interface system                                              | Yes                                          |
|                        | Logic level                                                               |                                              |
|                        | • Signal 0 [V]                                                            | ≤5                                           |
|                        | • Signal 1 [V]                                                            | ≥-11                                         |
| Digital outputs        | Input delay [ms]                                                          | Typically 3                                  |
|                        | Switching logic                                                           | PNP                                          |
|                        | Input characteristic curve                                                | To IEC 1131-2                                |

# AS-interface® components

Compact I/O modules and valve interfaces

FESTO

| General technical data                          |                                                               |                                                                                                                                                |
|-------------------------------------------------|---------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------|
| Type                                            |                                                               | ASI-4DI3DO-M12x2-5POL-Z                                                                                                                        |
| Digital outputs                                 | No. of outputs                                                | 3                                                                                                                                              |
|                                                 | Allocation of outputs                                         | Socket 3 with double allocation, socket 4 with single allocation                                                                               |
|                                                 | Version of the actuator connection                            | 4x M12, 5-pin                                                                                                                                  |
|                                                 | Power supply 24 V DC                                          | From the auxiliary power supply, "black" AS-interface cable                                                                                    |
|                                                 | Max. output current per channel [A]                           | 1.0, 2 outputs can be switched together                                                                                                        |
|                                                 | Operating voltage [V DC]                                      | 24 ±25%                                                                                                                                        |
|                                                 | Fuse protection for power output                              | Internal thermal short circuit protection for each output                                                                                      |
|                                                 | Protection against polarity reversal                          | For actuator supply 24 V/0 V                                                                                                                   |
|                                                 | Switching logic                                               | PNP                                                                                                                                            |
|                                                 | Output characteristic curve                                   | To ICE 1131-2                                                                                                                                  |
|                                                 | Electrical separation                                         |                                                                                                                                                |
|                                                 | • between the channels                                        | None                                                                                                                                           |
|                                                 | • to the AS-interface system                                  | Yes                                                                                                                                            |
|                                                 | Voltage drop across the output [V]                            | <1.5                                                                                                                                           |
|                                                 | Limitation of inductive switch-off voltage [V]                | –10 ... –45                                                                                                                                    |
|                                                 | LED displays                                                  |                                                                                                                                                |
| General data                                    | • Inputs                                                      | 4 green                                                                                                                                        |
|                                                 | • Outputs                                                     | 3 yellow                                                                                                                                       |
|                                                 | • AS-interface LED                                            | Power/green                                                                                                                                    |
|                                                 | • AUX-PWR-LED                                                 | Auxiliary power supply/green                                                                                                                   |
| AS-interface connection/load voltage connection | • FAULT-LED                                                   | Fault LED/red                                                                                                                                  |
|                                                 | Protection class to EN 60529                                  | IP65/IP67 (when fully plugged in or fitted with protective cap)                                                                                |
|                                                 | Material                                                      | Polybuteneterephthalate                                                                                                                        |
|                                                 | Dimensions (LxWxD) [mm]                                       | 151 x 30 x 30                                                                                                                                  |
|                                                 | Weight [g]                                                    | 165                                                                                                                                            |
|                                                 | Connection with the AS-interface                              | Via M12 connecting cables, 4-wire                                                                                                              |
|                                                 | Watchdog function                                             | Active after 50 ms                                                                                                                             |
|                                                 | Peripherals fault/diagnostics                                 | Short circuit/overload (thermal fuse on each channel) in accordance with specification C.S.2.1, two red fault LEDs<br>Automatic voltage return |
|                                                 | AS-interface bus voltage [V]                                  | 26.5 ... 31.6                                                                                                                                  |
|                                                 | Total current consumption of AS-interface [mA]                | Max. 250                                                                                                                                       |
|                                                 | Current-carrying capacity of M12 pins (AS-interface, AUX) [A] | Max. 4                                                                                                                                         |
|                                                 | AS-interface data                                             |                                                                                                                                                |
|                                                 | • IO code                                                     | 7 <sub>h</sub>                                                                                                                                 |
|                                                 | • ID code 1                                                   | A <sub>h</sub>                                                                                                                                 |
|                                                 | • ID code 2                                                   | 2 <sub>h</sub>                                                                                                                                 |
|                                                 | • Profile                                                     | S-7.A.2                                                                                                                                        |
|                                                 | AS-interface address (factory setting)                        | #0A                                                                                                                                            |
|                                                 | AS-interface specification                                    | 2.11 (compatible with 3.0)                                                                                                                     |

# AS-interface® components

Compact I/O modules and valve interfaces

FESTO

| Operating and environmental conditions        |                                                                   |             |
|-----------------------------------------------|-------------------------------------------------------------------|-------------|
| Type                                          | ASI-4DI3DO-M12x2-5POL-Z                                           |             |
| Protection class to DIN 60529                 | IP65/IP67 (when fully plugged-in or fitted with protective cover) |             |
| Ambient temperature                           | [°C]                                                              | –5 ... +50  |
| Storage temperature                           | [°C]                                                              | –20 ... +70 |
| Corrosion resistance class CRC <sup>1)</sup>  | 1                                                                 |             |
| CE mark (see declaration of conformity)       | To EU EMC Directive <sup>2)</sup>                                 |             |
|                                               | To EU Explosion Protection Directive (ATEX)                       |             |
| Certification                                 | c UL us - Listed (OL)                                             |             |
| Note on materials                             | Conforms to RoHS                                                  |             |
| Paint-wetting impairment substances criterion | PWIS-free                                                         |             |

- 1) Corrosion resistance class 1 as per Festo standard 940 070  
Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.
- 2) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: [www.festo.com/sp](http://www.festo.com/sp) → Certificates.  
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.


| Certifications ATEX              |                             |               |
|----------------------------------|-----------------------------|---------------|
| ATEX category gas                | II 3G                       |               |
| Ex-ignition protection type gas  | Ex nA IIC T4 X Gc           |               |
| ATEX category dust               | II 3D                       |               |
| EX-ignition protection type dust | Ex tc IIIC T115°C X Dc IP67 |               |
| ATEX ambient temperature         | [°C]                        | –5 ≤ Ta ≤ +50 |

 Note

For the operation of device combinations in hazardous areas, the lowest ambient temperature of the individual devices determine the common zone, temperature class and possible use of the entire module.


## Connection and display components

ASI-4DI3DO-M12x2-5POL-Z




- 1 AS-interface connection, incoming
- 2 Status LED (green)
- 3 Green LED for load voltage display
- 4 Green LED for status display (one LED per input)
- 5 Yellow LED for status display (one LED per output)
- 6 Red LED for short circuit/overload display
- 7 AS-interface connection, outgoing
- 8 Sensor connections
- 9 Outputs

## Pin allocation for sensor connections ASI-4DI3DO-M12X2-5POL-Z

| Pin allocation                                                                    | Pin | Signal  | Description               |
|-----------------------------------------------------------------------------------|-----|---------|---------------------------|
|  | 1   | 24 V DC | Operating voltage 24 V DC |
|                                                                                   | 2   | Ix*+1   | Sensor signal             |
|                                                                                   | 3   | 0 V     | Operating voltage 0 V     |
|                                                                                   | 4   | Ix*     | Sensor signal             |
|                                                                                   | 5   | Earth   | Earth terminal            |

\* Ix = Input x


## Pin allocation for outputs ASI-4DI3DO-M12X2-5POL-Z

| Pin allocation                                                                     | Outputs 1 and 2 |        |                       | Output 3 |        |                       |
|------------------------------------------------------------------------------------|-----------------|--------|-----------------------|----------|--------|-----------------------|
|                                                                                    | Pin             | Signal | Description           | Pin      | Signal | Description           |
|  | 1               | n.c.   | Not connected         | 1        | n.c.   | Not connected         |
|                                                                                    | 2               | Ox*+1  | Output                | 2        | n.c.   | Not connected         |
|                                                                                    | 3               | 0 V    | Operating voltage 0 V | 3        | 0 V    | Operating voltage 0 V |
|                                                                                    | 4               | Ox*    | Output                | 4        | Ox*+2  | Output                |
|                                                                                    | 5               | Earth  | Earth terminal        | 5        | Earth  | Earth terminal        |

\* Ox = Output


## Dimensions

### ASI-8DI-M8-3POL



Download CAD data → [www.festo.com](http://www.festo.com)





### ASI-4DI3DO-M12x2-5POL-Z



# AS-interface® components

Compact I/O modules and valve interfaces – Accessories



**FESTO**

| Ordering data                                                                       |                                                                                  |                               |          |                            |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------|-------------------------------|----------|----------------------------|
|                                                                                     | Description                                                                      |                               | Part No. | Type                       |
| Bus connection                                                                      |                                                                                  |                               |          |                            |
|    | AS-interface flat cable, yellow                                                  | 100 m                         | 18940    | KASI-1,5-Y-100             |
|                                                                                     | AS-interface flat cable, black                                                   | 100 m                         | 18941    | KASI-1,5-Z-100             |
|    | Cable cap for flat cable (scope of delivery 50 pieces)                           |                               | 18787    | ASI-KK-FK                  |
|    | Cable sleeve (scope of delivery 20 pieces)                                       |                               | 165593   | ASI-KT-FK                  |
|    | Socket M12, 4-pin                                                                | For AS-interface flat cable   | 18789    | ASI-SD-PG-M12              |
|                                                                                     |                                                                                  |                               |          |                            |
| Cable distributor                                                                   |                                                                                  |                               |          |                            |
|    | AS-Interface data to socket M12, 4-pin                                           |                               | 572225   | NEFU-X22F-M12G4            |
|   | AS-Interface data and load voltage supply to socket M12, 4-pin                   |                               | 572226   | NEFU-X24F-M12G4            |
|  | AS-Interface data and load voltage supply to socket M12, 4-pin, cable length 1 m |                               | 572227   | NEFU-X24F-1-M12G4          |
|                                                                                     |                                                                                  |                               |          |                            |
| T-type plug connector                                                               |                                                                                  |                               |          |                            |
|  | T-adapter for DH-485, M12 5-pin                                                  |                               | 171175   | FB-TA-M12-5POL             |
|  | Plug M12, A-coded, 4-pin                                                         | 2x socket M12, A-coded, 5-pin | 8005310  | NEDY-L2R1-V1-M12G5-N-M12G4 |
|                                                                                     |                                                                                  | 2x socket M8, A-coded, 3-pin  | 8005311  | NEDY-L2R1-V1-M8G3-N-M12G4  |
|  | Modular system for sensor/actuator distributor<br>➔ Internet: nedy               |                               | –        | NEDY-...                   |

# AS-interface® components

Compact I/O modules and valve interfaces – Accessories





FESTO

| Ordering data                                                                       |                                                                     |                       |          |                        |
|-------------------------------------------------------------------------------------|---------------------------------------------------------------------|-----------------------|----------|------------------------|
|                                                                                     | Description                                                         |                       | Part No. | Type                   |
| Connecting cables                                                                   |                                                                     |                       |          |                        |
|    | Modular system for connecting cables<br>➔ Internet: nebu            |                       | –        | NEBU-...               |
|                                                                                     | Straight plug M8, 3-pin, straight socket<br>M8, 3-pin               | 0.5 m                 | 541346   | NEBU-M8G3-K-0.5-M8G3   |
|                                                                                     |                                                                     | 1.0 m                 | 541347   | NEBU-M8G3-K-1-M8G3     |
|                                                                                     |                                                                     | 2.5 m                 | 541348   | NEBU-M8G3-K-2.5-M8G3   |
|                                                                                     |                                                                     | 5.0 m                 | 541349   | NEBU-M8G3-K-5-M8G3     |
|                                                                                     | Straight plug M12, 4-pin, straight socket<br>M12, 5-pin             | 0.5 m                 | 8000208  | NEBU-M12G5-K-0.5-M12G4 |
| DUO plugs                                                                           |                                                                     |                       |          |                        |
|    | Plug M12 for 2 sensor cables                                        | 4-pin, PG11           | 18779    | SEA-GS-11-DUO          |
|                                                                                     |                                                                     | 5-pin, PG11           | 192010   | SEA-5GS-11-DUO         |
| Sensor plugs                                                                        |                                                                     |                       |          |                        |
|    | Straight sensor plug                                                | M12, 5-pin, PG7       | 175487   | SEA-M12-5GS-PG7        |
|   | Straight sensor plug                                                | M12, 4-pin, PG7       | 18666    | SEA-GS-7               |
|                                                                                     | Straight sensor plug                                                | M12, PG9, 4-pin       | 18778    | SEA-GS-9               |
|  | Straight sensor plug for cable Ø 2.5 mm                             | M12, 4-pin            | 192008   | SEA-4GS-7-2,5          |
|  | Straight sensor plug                                                | M8, screw-in, 3-pin   | 192009   | SEA-3GS-M8-S           |
|  | Straight sensor plug                                                | M8, solderable, 3-pin | 18696    | SEA-GS-M8              |
|  | Cover cap (scope of delivery 10 pieces)                             | M12                   | 165592   | ISK-M12                |
|                                                                                     |                                                                     | M8                    | 177672   | ISK-M8                 |
| Miscellaneous                                                                       |                                                                     |                       |          |                        |
|  | Primary switched mode, modular power supply<br>24 V DC power supply | 5 A                   | 2247681  | CACN-3A-1-5            |
|                                                                                     |                                                                     | 10 A                  | 2247682  | CACN-3A-1-10           |
|  | Addressing device (power supply plug included in scope of delivery) |                       | 18959    | ASI-PRG-ADR            |
|  | Addressing cable                                                    |                       | 18960    | KASI-ADR               |

## AS-interface® components

Compact I/O modules and valve interfaces – Accessories

**FESTO**

| Ordering data                                                                      |                                                             |          |                         |
|------------------------------------------------------------------------------------|-------------------------------------------------------------|----------|-------------------------|
|                                                                                    | Description                                                 | Part No. | Type                    |
| I/O modules                                                                        |                                                             |          |                         |
|   | AS-interface input module for 8 inputs M8                   | 542124   | ASI-8DI-M8-3POL         |
|   | AS-interface input/output module for 4 inputs/3 outputs M12 | 542125   | ASI-4DI3DO-M12X2-5POL-Z |
| Mountings                                                                          |                                                             |          |                         |
|   | H-rail to EN 60715                                          | 35430    | NRH-35-2000             |
|   | Mounting for H-rail                                         | 170169   | CP-TS-HS35              |
| Inscription labels                                                                 |                                                             |          |                         |
|  | Inscription labels 8x20 mm in frames (20 pieces)            | 539388   | IBS-8x20                |


# AS-Interface® components

Addressing device

FESTO

## Addressing device ASI-PRG-ADR

- Parameterisation of AS-Interface components
- Display and editing of addresses, input and output signals
- Corresponds to AS-Interface SPEC 3.0



### Description

Before an AS-Interface network is commissioned, addresses must be assigned to the connected slaves. These addresses are stored in an EEPROM chip on each slave. Each slave is connected to the addressing device for the allocation of an address. Addressing is simple and is carried out using 5 keys.

The main advantages are:

- Compact design
- Can be addressed on-site
- Supports AS-Interface specification S-7.7.A.7 (SPEC 3.0), S-0.B and S-7.B (AS-Interface Safety at Work)

Using the addressing device according to SPEC 3.0, it is possible to scan the AS-Interface from any chosen point in the network. At all connected stations

- slave addresses can be read/changed
- ID and IO codes can be read out
- parameters can be read/changed
- input/output data can be read and written (setting outputs)
- error messages can be read out and quickly recognised

Independent of voltage supplies

- Battery operation

Simple reading of error codes

- LCD display

Reliable

- Short-circuit proof
- Overload-proof

Universal adapter connection suitable for a large number of AS-Interface slaves. Additional addressing cable for slaves with M12 round plug or flat-cable socket optionally available.

### General technical data

|                           |                 |
|---------------------------|-----------------|
| Display                   | LCD display     |
| Control elements          | Membrane keypad |
|                           | 5 keys          |
| No. of function keys      | 5               |
| Dimensions W x L x H [mm] | 34 x 210 x 80   |
| Product weight [g]        | 610             |

### Technical data – Electrical

|                                  |                 |
|----------------------------------|-----------------|
| Nominal operating voltage [V DC] | 28              |
| Permissible load current [mA]    | 100             |
| Power supply                     | Lithium battery |
| Short circuit protection         | Yes             |
| Overload protection              | Present         |

### Technical data – Fieldbus interface

|                       |                       |
|-----------------------|-----------------------|
| Protocol              | AS-Interface SPEC 3.0 |
| Connection type       | Socket                |
| Connection technology | M12x1, A-coded        |
| Number of pins/wires  | 5                     |
| Based on standard     | To EN 61076-2-101     |

# AS-Interface® components

Addressing device



| Materials         |                |
|-------------------|----------------|
| Housing           | PA reinforced  |
| Note on materials | RoHS compliant |

| Operating and environmental conditions                      |                                   |
|-------------------------------------------------------------|-----------------------------------|
| Ambient temperature [°C]                                    | 0 ... +40                         |
| Degree of protection                                        | IP20                              |
| CE marking<br>(see declaration of conformity) <sup>2)</sup> | To EU EMC Directive <sup>1)</sup> |

- 1) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: [www.festo.com/sp](http://www.festo.com/sp) → Certificates.  
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.
- 2) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)


1) LCD display, character height 13 mm

|             | B1 | H1  | H2 | L1 | L2 |
|-------------|----|-----|----|----|----|
| ASI-PRG-ADR | 34 | 210 | 35 | 80 | 43 |

| Ordering data |                   |          |             |
|---------------|-------------------|----------|-------------|
|               | Designation       | Part No. | Type        |
|               | Addressing device | 18959    | ASI-PRG-ADR |
|               | Addressing cable  | 18960    | KASI-ADR    |

## Overview of cables

### Addressing cable – KASI-ADR




The addressing cable ASI-ADR, available as an accessory, can be used to address any desired slaves either

directly via the flat cable connection (FK) or via the M12 connection (M12):

- Individual valve interface (FK)

- Compact I/O modules (M12)
- CPV valve terminals (FK)
- SPC11 Soft Stop (FK)

### Flat cable – KASI-1,5-...-100



KASI-1,5-Y-100 (yellow)


KASI-1,5-Z-100 (black)

The flat cable is of a 2-wire design. The coding profile prevents polarity reversal of the cable.

AS-interface network stations are connected to the flat cable via insulation displacement technology which utilises contact pins, thus eliminating the need to strip cable and wire insulation.

The yellow cable is normally used for the AS-interface network and the black cable for the auxiliary power supply.

### Connecting cable NEBU-M12...-M12...



The round cables are of a 4-wire design and are protected against polarity reversal. Standardised connection technology replaces the yellow/black AS-interface cable with a common cable.

- Fixed lengths: 0.2 m, 1 m, 2.5 m and 5 m ex-stock
- NEBU modular system for connecting cables



Note

Define your connecting cable yourself. Select M8 (3-pin or 4-pin) or M12 (4-pin or 5-pin) on each side as required and specify the required cable length and quality – Festo will then supply the exact cable you require.

➔ [www.festo.com](http://www.festo.com)


### Flat cable sleeve – ASI-KT-FK



For insulating and sealing the AS-interface cable at the end of the string

- Protection class IP65
- Shrinks on application of heat (hot air blower etc.)

### Cable cap – ASI-KK-FK




For insulating and sealing the AS-interface cable at the end of the string

- Protection class IP65

## Dimensions


Download CAD data → [www.festo.com](http://www.festo.com)

### Addressing cable – KASI-ADR




- 1 Round plug connector for connection to addressing device
- 2 Flat cable socket for connecting stations in the AS-interface network with plug-in connection
- 3 Flat cable socket with M12 connection plug for stations in the AS-interface network with M12 interface

### Flat cable – KASI-1,5-...-100




- 1 blue (-)
- 2 brown (+)

### Flat cable sleeve – ASI-KT-FK



### Cable cap – ASI-KK-FK




## Overview of connection components

### Flat cable socket


Flat cable socket for connecting AS-interface network stations to the flat cable. The connection is detachable.

The cable socket is protected against reverse polarity.




#### ASI-SD-FK

Flat cable socket for CPV valve terminals.




#### ASI-SD-FK180

Version FK180 for looping through of flat cable on top.



#### ASI-SD-FK-M12


Blanking plug for sealing unused connections for flat cable sockets.



#### ASI-SD-PG-M12


Flat cable socket with M12 connection and special seal for the flat cable in a PG connector. For compact input module (ASI-8DI-M8-3POL).

### Flat cable distributors



#### ASI-KVT-FK


Parallel flat cable distributor enables the flat cable to be branched at any desired point to the AS-interface network stations.



#### ASI-KVT-FK-S

Symmetrical flat cable distributor that enables the coding profile of the flat cable to be turned through 180° when changing cables. This avoids the need to install a loop. Three cable caps are provided in the scope of delivery to seal the cable ends.

### Cable distributor




#### NEFU-X2

Flat cable socket with M12 connection for looping through the flat cable. Can be plugged into 4-pin and 5-pin interfaces.

## Overview – Distributor

### T-type plug connector – NEDY




The sensor/actuator distributors combine two sensor signals (2x 3-pin cable) on one 4-pin plug. This is routed to the 4-pin or 5-pin input socket of a valve terminal or the

compact I/O module. Variants and cable lengths can be configured:

➔ Internet: nedy


### DUO plug – SEA-5GS11-DUO



The DUO plug combines two sensor or actuator signals/cables in one housing.

## Overview – Other connecting cables

### Extension cable – NEBU



The connecting cables can be used to extend the cable length between a distributor and the inputs of a valve terminal or a compact I/O module.


They can also be used as AS-interface bus cables for M12 connection technology.

Variants and cable lengths can be configured:

➔ Internet: nebu

## Overview – Other accessories


### Inscription labels IBS-...











Convenient labelling system for






- flat cable sockets
- flat cable distributors
- individual valve interfaces
- compact I/O modules
- CPV valve terminals






### H-rail NRH-35-2000



- For compact I/O modules
- CPV valve terminals
- For individual valve interfaces
- AS-interface power supply units

| Ordering data                                                                       |                                                                                  |                             |          |                   |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------|-----------------------------|----------|-------------------|
|                                                                                     | Description                                                                      |                             | Part No. | Type              |
| Bus connection                                                                      |                                                                                  |                             |          |                   |
|    | AS-interface flat cable, yellow                                                  | 100 m                       | 18940    | KASI-1,5-Y-100    |
|                                                                                     | AS-interface flat cable, black                                                   | 100 m                       | 18941    | KASI-1,5-Z-100    |
|    | Flat cable socket                                                                |                             | 18785    | ASI-SD-FK         |
|    | Flat cable socket                                                                | Turned through 180°         | 196089   | ASI-SD-FK180      |
|    | Flat cable blanking plug                                                         |                             | 196090   | ASI-SD-FK-BL      |
|    | AS-interface flat cable distributor                                              | Parallel cable              | 18786    | ASI-KVT-FK        |
|   | AS-interface flat cable distributor                                              | Symmetrical cable           | 18797    | ASI-KVT-FK-S      |
|  | Cable cap for flat cable (scope of delivery 50 pieces)                           |                             | 18787    | ASI-KK-FK         |
|  | Cable sleeve (scope of delivery 20 pieces)                                       |                             | 165593   | ASI-KT-FK         |
|  | Socket M12, 4-pin                                                                | For AS-interface flat cable | 18789    | ASI-SD-PG-M12     |
|  | Socket M12, 5-pin                                                                | For round cable             | 18324    | FBSD-GD-9-5POL    |
|                                                                                     |                                                                                  |                             |          |                   |
| Cable distributor                                                                   |                                                                                  |                             |          |                   |
|  | AS-Interface data to socket M12, 4-pin                                           |                             | 572225   | NEFU-X22F-M12G4   |
|  | AS-Interface data and load voltage supply to socket M12, 4-pin                   |                             | 572226   | NEFU-X24F-M12G4   |
|  | AS-Interface data and load voltage supply to socket M12, 4-pin, cable length 1 m |                             | 572227   | NEFU-X24F-1-M12G4 |

| Ordering data                                                                       |                                                                    |                               |          |                            |
|-------------------------------------------------------------------------------------|--------------------------------------------------------------------|-------------------------------|----------|----------------------------|
|                                                                                     | Description                                                        |                               | Part No. | Type                       |
| Sensor plugs                                                                        |                                                                    |                               |          |                            |
|    | Straight sensor plug                                               | M12, 5-pin, PG7               | 175487   | SEA-M12-5GS-PG7            |
|    | Straight sensor plug                                               | M12, 4-pin, PG7               | 18666    | SEA-GS-7                   |
|                                                                                     |                                                                    | M12, PG9, 4-pin               | 18778    | SEA-GS-9                   |
|    | Angled sensor plug                                                 | M12, 4-pin                    | 12956    | SIE-WD-TR                  |
|    | Straight sensor plug for cable Ø 2.5 mm                            | M12, 4-pin                    | 192008   | SEA-4GS-7-2,5              |
|                                                                                     | Straight sensor plug                                               | M8, screw-in, 3-pin           | 192009   | SEA-3GS-M8-S               |
|    | Straight sensor plug                                               | M8, solderable, 3-pin         | 18696    | SEA-GS-M8                  |
|    | Harax sensor plug                                                  | 4-pin                         | 525928   | SEA-GS-HAR-4POL            |
|  | Sub-D plug                                                         | 25-pin                        | 527522   | SD-SUB-D-ST25              |
|  | Cover cap (scope of delivery 10 pieces)                            | M12                           | 165592   | ISK-M12                    |
|                                                                                     |                                                                    | M8                            | 177672   | ISK-M8                     |
| DUO plugs                                                                           |                                                                    |                               |          |                            |
|  | Plug M12 for 2 sensor cables                                       | 4-pin, PG11                   | 18779    | SEA-GS-11-DUO              |
|                                                                                     |                                                                    | 5-pin, PG11                   | 192010   | SEA-5GS-11-DUO             |
| T-type plug connector                                                               |                                                                    |                               |          |                            |
|  | T-adaptor for DH-485, M12 5-pin                                    |                               | 171175   | FB-TA-M12-5POL             |
|  | Plug M12, A-coded, 4-pin                                           | 2x socket M12, A-coded, 5-pin | 8005310  | NEDY-L2R1-V1-M12G5-N-M12G4 |
|                                                                                     |                                                                    | 2x socket M8, A-coded, 3-pin  | 8005311  | NEDY-L2R1-V1-M8G3-N-M12G4  |
|  | Modular system for sensor/actuator distributor<br>➔ Internet: nedy |                               | –        | NEDY-...                   |

| Ordering data                                                                       |                                                                                  |                     |          |                        |
|-------------------------------------------------------------------------------------|----------------------------------------------------------------------------------|---------------------|----------|------------------------|
|                                                                                     | Description                                                                      |                     | Part No. | Type                   |
| Connecting cables                                                                   |                                                                                  |                     |          |                        |
|    | Modular system for connecting cables<br>➔ Internet: nebu                         |                     | –        | NEBU-...               |
|                                                                                     | Straight plug M8, 3-pin, straight socket<br>M8, 3-pin                            | 0.5 m               | 541346   | NEBU-M8G3-K-0.5-M8G3   |
|                                                                                     |                                                                                  | 1.0 m               | 541347   | NEBU-M8G3-K-1-M8G3     |
|                                                                                     |                                                                                  | 2.5 m               | 541348   | NEBU-M8G3-K-2.5-M8G3   |
|                                                                                     |                                                                                  | 5.0 m               | 541349   | NEBU-M8G3-K-5-M8G3     |
|                                                                                     | Straight plug M12, 4-pin, straight socket<br>M12, 5-pin                          | 0.5 m               | 8000208  | NEBU-M12G5-K-0.5-M12G4 |
| Connecting cable, straight plug, straight<br>socket                                 |                                                                                  | M12, 8-pin, 2.0 m   | 525617   | KM12-8GD8GS-2-PU       |
| Miscellaneous                                                                       |                                                                                  |                     |          |                        |
|    | Primary switched mode, modular power<br>supply                                   | 5 A                 | 2247681  | CACN-3A-1-5            |
|                                                                                     | 24 V DC power supply                                                             | 10 A                | 2247682  | CACN-3A-1-10           |
|   | Addressing device                                                                |                     | 18959    | ASI-PRG-ADR            |
|  | Addressing cable                                                                 |                     | 18960    | KASI-ADR               |
| Inscription labels                                                                  |                                                                                  |                     |          |                        |
|  | Inscription labels in frames                                                     | 8x20 mm (20 pieces) | 539388   | IBS-8x20               |
|                                                                                     |                                                                                  | 6x10 mm (64 pieces) | 18576    | IBS-6x10               |
|                                                                                     |                                                                                  | 9x20 mm (20 pieces) | 18182    | IBS-9x20               |
|  | Inscription label holder for connection block, transparent, for paper foil label |                     | 533362   | VMPA1-ST-1-4           |
|                                                                                     | Inscription label holder for connection block, 4-fold, for IBS 6x10              |                     | 544384   | VMPA1-ST-2-4           |
| Mounting accessories                                                                |                                                                                  |                     |          |                        |
|  | Mounting for H-rail                                                              |                     | 170169   | CP-TS-HS35             |
|  | Mounting for H-rail                                                              |                     | 526032   | CPX-CPA-BG-NRH         |
|  | H-rail to EN 60715                                                               |                     | 35430    | NRH-35-2000            |
|  | Mounting bracket                                                                 |                     | 534416   | VMPA-BG-RW             |