


Semi-rotary drive, metric DSR

FESTO



Characteristics

At a glance

- Double-acting semi-rotary drive with vane
- The swivel angle is infinitely adjustable over the entire swivel range
- The adjustable stop system is separate from the vane so that any forces are absorbed by the stop blocks
- The stops are cushioned in the end positions by elastic polymer pads.
- DSRL-...-FW: The versions with a hollow flange shaft allow liquid or gaseous media or tubing and electrical cables to be fed through. The force is transmitted directly and backlash-free via a splined shaft

Cushioning

[P]

Elastic cushioning rings/plates on both sides

The drive is fitted with elastic polymer end-position cushioning.


Shaft

[]

Spigot shaft

[FW]

Flanged shaft



Type code

001	Series	
DSRL	Semi-rotary drive	
DSR	Semi-rotary drive	

002	Size [mm]	
10	10	
12	12	
16	16	
25	25	
32	32	
40	40	

003	Nominal swivel angle [°]	
180	180	

004	Cushioning	
P	Elastic cushioning rings/plates on both sides	

005	Shaft	
	Spigot shaft	
FW	Flanged shaft	

Datasheet

General technical data

Size	10	12	16	25	32	40
Design	Vane					
Mode of operation	Double-acting					
Cushioning	Elastic cushioning rings/plates at both ends					
Cushioning angle	2.4 deg	2.2 deg	2.1 deg	1.8 deg	1.2 deg	0.9 deg
Position detection	Without					
Type of mounting	With through-hole					
Mounting position	optional					
Swivel angle	0 ... 180 deg					
Product weight	100 g	200 g	300 g	500 g	1,300 g	2,400 g

Operating and environmental conditions

Size	10	12	16	25	32	40
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]					
Operating pressure ¹⁾	2.5 ... 8 bar	2 ... 8 bar		1.5 ... 8 bar		
Ambient temperature ²⁾	-10 ... 60°C					

1) The minimum operating pressure can be increased by up to 0.5 bar after a rest period of 24 hours

2) Observe the operating range of the proximity switches

Weight

Size	10	12	16	25	32	40
Product weight	100	200	300	500	1,300	2,400

Materials

Material housing	Die-cast zinc
Material drive shaft	Steel, Nickel-plated
Material covering	PA-reinforced
Material seals	NBR
LABS (PWIS) conformity	VDMA24364-B2-L
RoHS status	RoHS compliant in accordance with EU directive

Forces and torques

Size	10	12	16	25	32	40
Theoretical torque at 0.6 MPa (6 bar, 87 psi)	0.5 Nm	1 Nm	2 Nm	5 Nm	10 Nm	20 Nm
Max. radial force ¹⁾	30 N	45 N	75 N	120 N	200 N	350 N
Max. axial force ²⁾	10 N	18 N	30 N	50 N	75 N	120 N
Max. swivel frequency at 0.6 MPa (6 bar, 87 psi)	3 Hz					

1) On the output shaft at max. frequency

2) On the output shaft at max. frequency

Assembly instructions

If the specified maximum permissible mass moments of inertia are exceeded, external stops must be used. The following must be noted in this case:

The stop must not fall below a minimum radius to the output shaft (r_{min}). The stop force must not exceed the maximum force. Because of the elastic stops, an exact end position can only be achieved using an external stop.

Size 10: Stop radius 13 mm / force 60 N

Size 12: Stop radius 15 mm / force 90 N

Size 16: Stop radius 17 mm / force 160 N




Size 25: Stop radius 21 mm / force 320 N

Size 32: Stop radius 28 mm / force 480 N

Size 40: Stop radius 40 mm / force 650 N


If the semi-rotary drives are throttled to swivel speeds below 180°/s, the drives must be operated with a minimum of 6 bar. A synchronisation fluctuation of $\pm 30\%$ is to be expected. An improvement in the synchronisation fluctuations and the swivel times shown in the graphs can only be achieved with throttle valves.

Datasheet


Mass moment of inertia m as a function of swivel time t and swivel angle for DSR/DSRL-10Mass moment of inertia m as a function of swivel time t and swivel angle for DSR/DSRL-12Mass moment of inertia m as a function of swivel time t and swivel angle for DSR/DSRL-16

Datasheet


Mass moment of inertia m as a function of swivel time t and swivel angle for DSR/DSRL-25



Mass moment of inertia m as a function of swivel time t and swivel angle for DSR/DSRL-32




Mass moment of inertia m as a function of swivel time t and swivel angle for DSR/DSRL-40



Dimensions

Dimensions – Quarter turn actuator DSR

Download CAD data www.festo.com

- [1] Angle scale for reading the swivelling angle
- [2] Featherkey position at 0°
- [3] Compressed air supply port
- [4] The swivel angle is 180° and is pressure-dependent. The maximum cushioning angle per side is approx. 1.6° at 8 bar
- [5] If, at the end of the swivelling motion, the kinetic energy is absorbed by the cushioning, the drive shaft will swivel back by a corresponding proportion of the angle.
- [6] The stops must not be removed, as the vane itself is not suitable for setting the end position. An angle scale is provided on the cover cap to help set the swivel angles.
- [7] The maximum permissible tightening torque of the bolt at D4 must not be exceeded when attaching additional components to the spigot shaft.

Dimensions

	B1	B2	B3	D1 Ø g7	D2 Ø	D3 Ø h9	D4	E1	E2	H1	H2	H3	L1	L2
DSR-10	22	32	53	6	12	20	M2,5	M3	M3	19,4	15,5	38,8	57	22,4
DSR-12	26	40	65	8	16	22	M3	M5	M3	23,5	18,5	48	65,6	25,5
DSR-16	30	46	78	10	17	24	M3	M5	M3	27	20,5	56,5	75,8	29
DSR-25	42	60	98	12	18	28	M4	M5	M4	30	23	68,1	94,5	35,4
DSR-32	54	80	130	16	27	42	M5	G1/8	M4	43	34	92	125,5	50
DSR-40	70	100	160	20	36	52	M6	G1/4	M4	53	40	121	162	60

	L3	L4	L5	L6	L7	S1	S2	T2	X	1)	2)
DSR-10	6,5	4,5	15,1	2,2	2	3,4	6	7	0,35	A2 x 2 x 12	0,7
DSR-12	5,5	3,5	18	2,1	2,5	4,4	8	9	0,35	A2 x 2 x 16	1,2
DSR-16	6	3,5	22,5	2,1	–	5,5	10	9	0,35	A3 x 3 x 18	1,2
DSR-25	5,4	3	30	4	–	7	11	10	0,4	A4 x 4 x 25	5,5
DSR-32	10	7	36	4	–	8,5	15	12,5	0,45	A5 x 5 x 36	5,5
DSR-40	10	6	50	4	–	8,5	15	16	0,5	A6 x 6 x 45	5,5


1) Feather key according to DIN 6885 included in the scope of delivery

2) Tightening torque at D4 [Nm]

Dimensions

Dimensions – Semi-rotary drives DSRL

Download CAD data www.festo.com



- [1] Angle scale for reading the swivelling angle
- [2] Featherkey position at 0°
- [3] Compressed air supply port
- [4] Through-hole
- [5] The swivel angle is 180° and is pressure-dependent. The maximum cushioning angle per side is approx. 1.6° at 8 bar
- [6] If, at the end of the swivelling motion, the kinetic energy is absorbed by the cushioning, the drive shaft will swivel back by a corresponding proportion of the angle.
- [7] The stops must not be removed, as the vane itself is not suitable for setting the end position. An angle scale is provided on the cover cap to help set the swivel angles.
- [8] The maximum permissible tightening torque of the bolt at D4 must not be exceeded when attaching additional components to the spigot shaft.

Dimensions


	B1	B2	B3	D1 ∅ g7	D2 ∅	D3 ∅ h8	D4	D5 ∅ f8	D6 ∅	D7 ∅ H13	D8 ∅ min.	E1	E2	E3	H1
DSRL-10	22	32	53	30	10	20	M3	11	21	3,4	1,5	M3	M3	M3	19,4
DSRL-12	26	40	65	33	13	22	M3	14	25	3,4	1,5	M5	M3	M3	23,5
DSRL-16	30	46	78	38	14	24	M5	16	28	4,5	3,5	M5	M3	M4	27
DSRL-25	42	60	98	46	17	28	M5	20	35	5,5	3,5	M5	M4	M5	30
DSRL-32	54	80	130	60	24	42	G1/8	28	45	6,5	7	G1/8	M4	M6	43
DSRL-40	70	100	160	70	30	52	G1/8	36	54	9	7	G1/4	M4	M8	53

	H2	H3	L1	L2	L3	L4	L5	L6	L7	L8	S1	S2	T1	X	1)
DSRL-10	15,5	38,8	49	14	12,3	4,5	15,1	3	2,2	2	3,4	6	5	0,35	0,7
DSRL-12	18,5	48	54,2	13,5	11,5	3,5	18	3	2,1	2,5	4,4	8	5	0,35	1,2
DSRL-16	20,5	56,5	64,7	16	14	3,5	22,5	4	2,1	–	5,5	10	6	0,35	1,2
DSRL-25	23	68,1	78	18,5	15,5	3	30	4,5	4	–	7	11	6	0,4	5,5
DSRL-32	34	92	102,8	26	22	7	36	6	4	–	8,5	15	8	0,45	5,5
DSRL-40	40	121	134,5	31	26	6	50	7,5	4	–	8,5	15	8	0,5	5,5

1) Tightening torque at D4 [Nm]

Dimensions


Dimensions – Foot mounting HSR-...-FW

Download CAD data www.festo.com

	B1	B2	D1 Ø H13	D2	D10	H1	H2	L1	L2	L3	N1
HSR-10-FW	53,5	43	3,5	2	20	4	53	11	17	21	34
HSR-12-FW	64	52	3,5	2	22	4	63	11	17	21	40
HSR-16-FW	77	63	5,7	2	24	5	71	14	22	26,5	44
HSR-25-FW	97	80	6,8	3	28	5	76	16	28	34	47
HSR-32-FW	129	105	8,8	4	42	8	108	20	34	43	66
HSR-40-FW	159	130	8,8	5	52	8	134	25	42	52	81

Dimensions


Dimensions – Flange mounting FSR Download CAD data www.festo.com



	B3	B4	D3 ø min.	D4	D5 ø H13	D6 ø H13	H3	L4 max.	N2	R
FSR-10	28	46	13	M3	3,4	6,5	7	2	20	18
FSR-12	31	54	17	M3	3,4	6,5	7	2	22	20,5
FSR-16	35	62	19	M4	4,5	8,5	8	2	26,5	23,5
FSR-25	40	76	21	M5	5,5	10,4	8	2,5	29	27
FSR-32	56	100	32	M6	6,6	12,4	12	2,5	42	36
FSR-40	72	120	37	M8	9	16,4	14	4	52	46

Dimensions


Dimensions – Push-on flange FWSR

[Download CAD data](#) www.festo.com


	B5	D4	D5 Ø H13	D7 Ø f8	D8 -0,5	D9 +0,4	L5	L6	L7
FWSR-10	21	M3	3,4	11	30	12	22	3	1,6
FWSR-12	25	M3	3,4	14	35	15	25	3	3
FWSR-16	28	M4	4,5	16	40	17	28	5	3
FWSR-25	35	M5	5,5	20	50	23	38	8	3
FWSR-32	45	M6	6,5	28	60	28	48	10	4
FWSR-40	54	M8	9	36	70	38	60	11	5

Dimensions

Dimensions – Free wheel unit FLSR

Download CAD data www.festo.com

	B4	B5	B6	D1 ø g7	D3 ø h8	D4	D5 ø H13	D6	H4	H5
FLSR-10	38	45	38,5	6	20	–	3,3	M3	20	42,5
FLSR-12	42	49	41,5	8	25	M3	3,3	M3	24	48,5
FLSR-16	50	60	50	10	24	M3	4,5	M4	28	58
FLSR-25	60	75	60	12	28	M4	6,6	M6	31	68,5
FLSR-32	83	98	83	16	42	M5	6,6	M6	44	93
FLSR-40	96	114	96	20	52	M6	8,6	M8	54	111


	L6	L7	L8	L9	L10	T1	T2	T3	T4	T5	1)
FLSR-10	3,5	4,2	41,5	20,2	23	6,8	8	8	5	8	A2 x 2 x 12
FLSR-12	3,5	4,5	47,3	24,5	25	8,8	9	8	5	9	A2 x 2 x 16
FLSR-16	3,5	4,4	47	27,4	23,5	11,2	11	10	8	11	A3 x 3 x 18
FLSR-25	3,5	4,1	48	34	24	13,5	14	12	11	14	A4 x 4 x 25
FLSR-32	7,2	8,5	60	48,5	30	18	16	12	11	16	A5 x 5 x 36
FLSR-40	6	8	75	58	38	22,5	21	15	11	21	A6 x 6 x 45

1) Feather key according to DIN 6885 included in the scope of delivery

Dimensions

Dimensions – Mounting kit WSR-12 ... 40 for micro stem actuated valve S-3-
PK-3-B, SO-3-PK-3-B

Download CAD data www.festo.com




	B1	B2	B3	H1	H2	L2	L3
WSR-12	5,8	23,4	4	1,5	23	14	79
WSR-16	10	26,5	4,5	1,5	29,8	19	84,5
WSR-25	12	29	2	1,5	38	24,5	90
WSR-32	12	29	2	1,5	49,2	40,5	107
WSR-40	12	29	2	1,5	68,7	52	118,5

Dimensions

Dimensions – Mounting kit WSR-...-J for proximity switch SIEN-M8; mounting kit WSR-...-J-M5 for proximity switch SIEN-M5

Download CAD data www.festo.com



	B4	H3	H4	L4	L5
WSR-16-J	13	1,5	35	52	27
WSR-25-J	13	1,5	43,1	52	34
WSR-32-J	13	1,5	54,3	64	48
WSR-40-J	13	1,5	76,3	80	60

	B4	H3	H4	L4	L5
WSR-10-J-M5	8	1	25,4	30	20
WSR-12 J-M5	8	1	28,3	34	24,5
WSR-16 J-M5	8	1	34,9	38	27
WSR-25 J-M5	13	1,5	43	52	34
WSR-32 J-M5	13	1,5	54,3	64	48
WSR-40 J-M5	13	1,5	76,3	80	60

Ordering data


With spigot shaft

	Size	Part no.	Type
	10	33297	DSR-10-180-P
	12	11909	DSR-12-180-P
	16	11910	DSR-16-180-P
	25	11911	DSR-25-180-P
	32	11912	DSR-32-180-P
	40	13467	DSR-40-180-P

With flanged shaft


	Size	Part no.	Type
	10	33296	DSRL-10-180-P-FW
	12	30654	DSRL-12-180-P-FW
	16	30655	DSRL-16-180-P-FW
	25	30656	DSRL-25-180-P-FW
	32	30657	DSRL-32-180-P-FW
	40	30658	DSRL-40-180-P-FW


Peripherals




Accessories		→ Link
Type/order code	Description	
[1] Semi-rotary drive DSR	Pneumatic drive	dsr
[2] Mounting kit WSR...	For proximity switch SIEN	20
[3] Proximity switch SIEN	Inductive proximity sensor, round design	21
[4] Micro stem actuated valve SO-3-PK-3-B, S-3-PK-3-B	Pneumatic, either normally open or normally closed	21
[5] Mounting kit	For micro stem actuated valve SO-3-PK-3-B, S-3-PK-3-B	20
[6] One-way flow control valve GRLA	For controlling speed	21
[7] Push-in fitting QSL	For connecting compressed air tubing with standard O.D.	qs
[8] Foot mounting HSR...-FW	On the output side	19
[9] Flange mounting FSR	On the output side	19
[10] Push-on flange FWSR	For spigot shaft	19
[11] Freewheel FLSR...-L/R	For spigot shaft, optional left/right swivel	20


Accessories

Foot mounting HSR					
	Description	Material bracket	Product weight	Part no.	Type
	For Ø 10	Steel	61 g	33317	HSR-10-FW
	For Ø 12		87 g	30923	HSR-12-FW
	For Ø 16		170 g	30924	HSR-16-FW
	For Ø 25		235 g	30925	HSR-25-FW
	For Ø 32		660 g	30926	HSR-32-FW
	For Ø 40		1,040 g	30927	HSR-40-FW

Flange mounting FSR					
	Description	Material plate	Product weight	Part no.	Type
	For Ø 10	Cast aluminium	22 g	34480	FSR-10
	For Ø 12		32 g	14658	FSR-12
	For Ø 16		50 g	13236	FSR-16
	For Ø 25		70 g	13237	FSR-25
	For Ø 32		180 g	13238	FSR-32
	For Ø 40		300 g	14655	FSR-40

Push-on flange FWSR					
	Description	Material housing	Product weight	Part no.	Type
	For Ø 10	Wrought aluminium alloy	10 g	32798	FWSR-10
	For Ø 12		19 g	14659	FWSR-12
	For Ø 16		30 g	13239	FWSR-16
	For Ø 25		70 g	13240	FWSR-25
	For Ø 32		120 g	13241	FWSR-32
	For Ø 40		240 g	14656	FWSR-40

FLSM-....-R right-hand rotation (clockwise)




The free wheel unit only allows movement in one of the two possible swivel directions of the semi-rotary drive DSR. The reverse direction is blocked.

This turns the oscillating swivel motion of the semi-rotary drive into a smooth, synchronous movement.

The minimum switchable swivel angle is 0.4°. The switching accuracy also depends on the switching speed and the load.

The load must be stopped externally

FLSM-....-L left-hand rotation (anti-clockwise)




The free wheel unit only allows movement in one of the two possible swivel directions of the semi-rotary drive DSR. The reverse direction is blocked.


This turns the oscillating swivel motion of the semi-rotary drive into a smooth, synchronous movement.


The minimum switchable swivel angle is 0.4°. The switching accuracy also depends on the switching speed and the load.


The load must be stopped externally

Accessories


Free wheel unit FLSR							
	Description	Direction of rotation	Theoretical torque at 0.6 MPa (6 bar, 87 psi)	Material housing	Product weight	Part no.	Type
	For Ø 10	Clockwise rotation	0.53 Nm	Die-cast aluminium	100 g	33299	FLSR-10-R
		Anticlockwise rotation				33298	FLSR-10-L
	For Ø 12	Clockwise rotation	1 Nm		220 g	30929	FLSR-12-R
		Anticlockwise rotation				30930	FLSR-12-L
	For Ø 16	Clockwise rotation	2.03 Nm		350 g	15280	FLSR-16-R
		Anticlockwise rotation				15281	FLSR-16-L
	For Ø 25	Clockwise rotation	4.95 Nm		500 g	13730	FLSR-25-R
		Anticlockwise rotation				13778	FLSR-25-L
	For Ø 32	Clockwise rotation	9.98 Nm		1,120 g	15687	FLSR-32-R
		Anticlockwise rotation				15688	FLSR-32-L
	For Ø 40	Clockwise rotation	20.03 Nm		1,820 g	19036	FLSR-40-R
		Anticlockwise rotation				19037	FLSR-40-L

Mounting kit WSR for micro stem actuated valve			
	Description	Part no.	Type
	For Ø 12	15684	WSR-12
	For Ø 16	14874	WSR-16
	For Ø 25	14796	WSR-25
	For Ø 32	14960	WSR-32
	For Ø 40	14961	WSR-40


Mounting kit WSR-...-J-M5 for proximity switch SIEN-M5			
	Description	Part no.	Type
	For Ø 10	33413	WSR-10-J-M5
	For Ø 12	15685	WSR-12-J-M5
	For Ø 16	15931	WSR-16-J-M5
	For Ø 25	15932	WSR-25-J-M5
	For Ø 32	15933	WSR-32-J-M5
	For Ø 40	15934	WSR-40-J-M5

Mounting kit WSR-...-J for proximity switch SIEN-M8			
	Description	Part no.	Type
	For Ø 16	14873	WSR-16-J


Accessories

Mounting kit WSR-...-J for proximity switch SIEN-M8			
	Description	Part no.	Type
	For Ø 25	14799	WSR-25-J
	For Ø 32	14962	WSR-32-J
	For Ø 40	14963	WSR-40-J

Micro stem actuated valve S-3-PK for DSR-16 ... 40					
	Valve function	Operating pressure	Product weight	Part no.	Type
	3/2-way, closed, monostable	-0.95 ... 8 bar	7 g	7843	S-3-PK-3-B
	3/2 open, single solenoid			10403	SO-3-PK-3-B

Proximity switch SIEN, inductive - for DSR-10 ... 40						Link sien
	Type of mounting ¹⁾	Switching output	Electrical connection	Cable length	Part no.	Type
	Via lock nut	PNP	Open end	2.5 m	150370	SIEN-M5B-PS-K-L
			Plug M8, A-coded		150371	SIEN-M5B-PS-S-L

1) With sensor bracket SL-DSM-S

Proximity switch SIEN, inductive – for DSR-16 ... 40						Link sien
	Type of mounting ¹⁾	Switching output	Electrical connection	Cable length	Part no.	Type
	Via lock nut	PNP	Open end	2.5 m	150386	SIEN-M8B-PS-K-L
			Plug M8, A-coded		150387	SIEN-M8B-PS-S-L

1) With sensor bracket SL-DSM-S

One-way flow control valves GRLA					
	Pneumatic connection 1	Pneumatic connection, port 2	Product weight	Part no.	Type
	Push-in connector 3 mm	M3	7 g	175041	GRLA-M3-QS-3
		M5	13 g	193137	GRLA-M5-QS-3-D
		G1/8	22 g	193142	GRLA-1/8-QS-3-D
	Push-in connector 4 mm	G1/8	13 g	★ 193138	GRLA-M5-QS-4-D
			22 g	193143	GRLA-1/8-QS-4-D
	Push-in connector 6 mm	G1/4	42 g	★ 193144	GRLA-1/8-QS-6-D
			42 g	★ 193146	GRLA-1/4-QS-6-D
	Push-in connector 8 mm	G1/8	22 g	★ 193145	GRLA-1/8-QS-8-D
	Push-in connector 10 mm	G1/4	42 g	★ 193147	GRLA-1/4-QS-8-D
				193148	GRLA-1/4-QS-10-D