

AS-interface® components


**FESTO**



# AS-interface® components

Overview of AS-interface

FESTO



# AS-interface® components

Overview of AS-interface

FESTO

## Basic principles and features of the bus system

### Introduction

AS-interface is a non-proprietary, open installation system with a large and growing share of the market at the lowest level of the decentralised production and process automation hierarchy.

The non-proprietary and open characteristics of the system are guaranteed by the European standard EN 50295 and the international

standard IEC 62026-2. Certified products bear the logo of the AS-International Association.

The AS-International Association and its affiliated organisations represent the interests of all manufacturers with an interest in the AS-interface.

### Design

The AS-interface system permits the transfer of power and data using a single cable. The advanced technology used to connect stations to the yellow cable and the low connection costs mean that even stations with a small number of inputs and outputs (max. 8 inputs and 8 outputs per valve terminal with two chips) can be networked. Reductions in installation costs of between 26% and 40% have been demonstrated depending on the system type. This solution is an ideal low-cost option for connecting individual or

small groups of actuators, valves and sensors to a master controller. New developments as per Specification V2.1 published at the start of 2000 such as the parameterisable profile 7.4 or the AS-interface Safety at Work concept opened the way for new areas of application and facilitated considerably more efficient installation and networking concepts in many instances.

Specification V3.0 published in 2005 represents another giant leap forward, facilitating convenient activation of

analogue I/O, complex slaves or serial text and data transfer, for example.

- Slaves as per Specifications V2.0 and V2.1 will also run under V3.0 – the system is fully downwards compatible. Benefits of AS-interface Specification V3.0:
- All of the benefits of the simple installation system since Specification V2.0 are retained
- Up to 400% more I/Os per master
- Improved peripheral error diagnostics
- More functions within Specifications V2.1 and V3.0, e.g. easy integration of complex 16-bit slaves,

fast analogue modules, DTM integration, asynchronous serial protocol, safety slaves

- Slave profiles for specific functions as well as interchangeability. Mix of different vendors and products, e.g. for parameters or communication services

AS-interface with A/B mode gives you 100% more. In A/B mode, each slave address is used twice. An output bit is used for A/B address differentiation (see table for case distinctions). The cycle time for pneumatic chains is generally more than adequate.

Specification Version	Inputs	Outputs	Bus cycle (ms)	No. of slaves, digital	No. of slaves, analogue	Σ I/O
2.0	4/4	4	5	31	31	248
2.1	4	3	10	62	31	434
3.0	4/8	4/8	20	62	62	992

### Master-slave principle

- Non-proprietary
- No restrictions in terms of cable layout and/or topology
- Data and power via a single two-wire cable
- Immune to interference
- Medium: unscreened cable 2x 1.5 mm<sup>2</sup>
- With 31 slaves, max. 4 inputs and 4 outputs per slave
- Data and power supply for up to 8 outputs per AS-interface string
- With 62 slaves, max. 4 inputs and 3 outputs per slave (A/B mode as per Specification V2.1)
- Modules for control cabinets (IP20) and harsh industrial environments (IP65, IP67)
- With 31 slaves, 4 analogue inputs or outputs per slave
- Profile 7.3: analogue values (16 bits) per slave (as per Specification V2.1)
- Profile 7.4: parameterisable communication profile, e.g. 16x 16 bits per slave (as per Specification V2.1)
- Profile 7.A.7 allows 4 bits for digital inputs and 4 bits for digital outputs on just one A/B slave. The 4 outputs are transmitted in two A/B bus cycles of 2 bits each. This extends the cycle time (in the worst-case scenario) to 20 ms.
- Insulation displacement technology
- Cable length 100 m, can be extended to up to 200 m through the use of an extension plug and to up to 500 m through the use of repeaters, etc.
- Highly effective error control
- Simple commissioning
- Electronic address selection via the bus connection



Note

Slaves to Specification V3.0 require a master to Specification V3.0

➔ Info 213 Valve terminal CPV

# AS-interface® components

Overview of AS-interface

**FESTO**

## Basic features

### Simple connection technology

- One cable for power and data
- Cable profile prevents polarity reversal
- Error control means there is no need for screening
- Insulation displacement connection technology guarantees Festo plug and work
- Alternative bus connection technology M12, 4-pin (standardised)

### Ideal for pneumatic applications

- Local control of small groups of actuators or individual distributed actuators covering an extensive area with
- short tubing lengths,
  - high cycle rates,
  - low air consumption.
- Installation and communication are carried out via AS-interface components.

### A powerful system component

AS-interface is clearly subordinate to the fieldbuses already in use and is therefore less a competing product and more a technically necessary and economically advisable add-on.

### Everything from a single source

- Festo is your single source for the AS-interface. This means
- one contact person,
  - competent solutions from the market leader,
  - convenient ordering system,
  - complete delivery service,
  - co-ordinated solutions for motion and control,
  - worldwide service round the clock.

## Optimised cycle rates

Decentralised solutions at the AS-interface permit optimised electro-pneumatic control loop systems: valve response times and optimum pairings of cylinder diameter and stroke save up to

- 20% cycle time with standard components
- 30% cycle time with fast switching valves
- 40% installation costs
- 50% air consumption/flow rate

## Product range overview

### Valves

- Integrated inputs on valve terminals CPV, MPA-S and VTSA/VTSA-F
- More inputs thanks to 4-fold and 8-fold input modules
- On request: Application-specific valves and integration solutions

### Gateways


- AS-interface gateways CESA as master within the AS-interface network and slave within a fieldbus network.
- PROFIBUS
  - CANopen




# AS-interface® components

System overview

FESTO



## Application examples



### Sorting

Valve terminals MPA-S, VTSA/VTSA-F and CPV:  
Compact Performance is synonymous with high performance and low


weight. Mounting close to the drives simplifies installation, saves compressed air and increases the cycle rates.



### Conveyor technology

Individually distributed drives and sensors covering an extensive area are common features of conveyor systems. The AS-interface is particularly suited to systems of this type.


Compact I/O modules support the direct connection of one or two valves of any size and up to 4 sensors to the AS-interface.



### Packaging

More complex machines frequently require decentralised installation concepts within the system in order to achieve an efficient electrical installation.

The AS-interface controls complex modules and upstream functions such as packaging in this picture.



### Assembling

Assembly, moving, handling: this often means rapid-fire sequences, tight installation spaces and the need for reduced weight.

Compact I/O modules, valve terminals and matching drives provide the optimum solution here.



### Process engineering

Water treatment  
Automation and decentralised intelligence are innovative features of newer systems.  
A compact I/O module is suitable for all valves with Namur interface. The


VTSA/VTSA-F valve terminal provides new scope for flow processes in 24-hour non-stop mode. Vertical pressure shut-off plates enable valve replacement under pressure (hot-swap) and thus avoid downtime.

# AS-interface® components

System overview

FESTO

## Master



AS-interface gateways are used to connect the AS-interface network to a higher-level fieldbus. They behave like a master within the AS-interface network and a slave within the fieldbus network.

AS-interface gateways from Festo conform to the AS-interface Specification 3.0 and support the extended addressing range with up to 62 AS-interface slaves.

Versions


- CANopen
- PROFIBUS

## Slaves

### Valves

- Simple solution incorporating compact EA modules
- Integrated inputs on valve terminals CPV, MPA-S and VTSA/VTSA-F
- More inputs thanks to 4-fold and 8-fold input modules
- On request: Application-specific valves and integration solutions


## Accessories



- Addressing device with user-friendly operating and diagnostic functions for the entire AS-interface, for example to perform the following tasks in a fully installed network:
  - change addresses
  - set outputs
  - read inputs
  - and many more
- Power supply unit for AS-interface
- Primary switched mode modular power supply
- Compact, modular and energy-saving power supply system for AS-interface – with integrated earth-fault monitoring system. Load: 5 or 10 A
- Installation accessories for installing the flat cable

## Valve interface variants

### Bus node CTEU




Incorporation of a range of valve terminals with I-Port interface in the AS-Interface:

- VTUG
- CPV

- VTUB-12
- VTOC
- MPA-L
- Universal connection technology M12

- Optional decentralised installation of the bus node with electrical connection box CAPC
- Basic diagnostics: undervoltage, short circuit

### Compact valve terminal CPV




Maximum performance of 400 ... 1600 l/min with minimal space requirement

- Valve combinations of 2, 4 or 8 valve slices
- Vacuum generation, relays and

- more in one unit
- Smart tubing system via pneumatic multiple connector plate:
  - Rapid replacement of valve terminals
  - With control cabinet installation:

- no internal tubing required
- M8 inputs included for each valve position
- Ex Zone 2, 22
- ASI Specification V2.0, V2.1 or V3.0

### Modular, multi-functional valve terminal MPA-S




- Valves on a sub-base: individual valves can be easily replaced
- MPA-S: sturdy and modular from 360 ... 700 l/min
- Flexible valve combinations for 2 ... 8 solenoid coils
- Valve terminals can be expanded at a later date

- Mix of MPA1/2 on a valve terminal possible for optimised flow rates and control loop systems
- All valve functions, regulators and pressure gauges for variable pressure adjustment per valve position.
- 4 or 8 inputs with selectable connection technology

- Selectable connection technology on the bus. Flat cable in the case of the 4E4A version or M12 round cable in the case of the 4E4A and 8E8A versions (where 'E' stands for inputs and 'A' outputs)

### Modular, multi-functional valve terminal VTSA/VTSA-F




- Standard valves 18, 26, 42 and 52 mm to ISO 17504-2 and 5599-2 on a sub-base: individual valves can be easily switched
- VTSA/VTSA-F: compact and modular from 550 ... 1500 l/min
- Flexible valve combinations for 1 ... 8 solenoid coils
- Valve terminals can be expanded at a later date

- Mix of 3 valve sizes on a valve terminal possible for optimised flow rates and control loop systems
- All valve functions, multiple pressure zones, regulators and pressure gauges for precision pressure adjustment per valve position, flow control, pressure shut-off plates for valve replacement under pressure (hot-swap) and additional components for vertical stacking

- 4 or 8 inputs with selectable connection technology
- Selectable connection technology on the bus. Flat cable in the case of the 4E4A version or M12 round cable in the case of the 4E4A and 8E8A versions (where 'E' stands for inputs and 'A' outputs)

### Compact I/O modules, valve interfaces



- Highly compact modules
- Sturdy, encapsulated electrics
- Bus and auxiliary power supply 2x M12 looped through

- Inputs 200 mA
- Outputs 1 A

- 8 inputs M8
- 4 inputs and 3 outputs M12

## AS-interface® components

CESA AS-interface modules

FESTO



### CESA AS-interface modules

AS-interface gateways are an ideal way of connecting decentralised AS-interface networks to higher-level controllers via a fieldbus. They enable system parts to be set up decentrally and combined into logical units.

#### General

- Extended AS-interface diagnostic functions
- Simple configuration error history
- Error counters for monitoring the quality of data communication on the AS-interface cable

#### Versions

- PROFIBUS and CANopen
- Extended addressing range, up to 62 AS-interface slaves
- Terminal strip connection technology
- LCD display and LEDs
- Conforms to AS-interface Specification 3.0

#### Application

- Interface between centralised controller with fieldbus interface and valve terminals and input/outputs with AS-i interface


# AS-interface® components

FESTO

CESA AS-interface modules – Connection technology and addressing

## Handling

### Mounting



The gateway is mounted using an H-rail. There are appropriate lugs on the rear of the device.

### Extended addressing range


The extended addressing range enables a total of 62 slaves to be operated on an AS-interface master. The masters as well as the slaves must be designed for the extended addressing range in order to be able to exploit the full number of slaves.

With the extended addressing range, two slaves share one address. Standard slaves do not have this capability. They can be connected to a master

with an extended addressing range, but also occupy a full address. In other words, up to 62 slaves with an extended addressing range but only 31 standard slaves can be connected to a master with an extended addressing range.

Slaves with an extended addressing range can, like standard slaves, be connected to a standard master, but must be configured as an "A" slave.

## AS-interface connections



The AS-interface network as well as the power supply for the gateway and AS-interface are connected via a terminal strip.

# AS-interface® components

CESA AS-interface modules

FESTO

General technical data			
		CESA-GW-AS-PB	CESA-GW-AS-CO
Operating elements		4 buttons	
Status displays		LCD display	
		Yellow LED: Projection mode	
		Green LED: AS-interface operating normally	
		Green LED: AS-interface voltage OK	
		Green LED: PROFIBUS master detected	
		Green LED: Slave programming	
		Green LED: Voltage ON	
		Red LED: Configuration error	
Operating voltage	[V DC]	30 (AS-interface voltage)	
Current consumption	[mA]	200 (from the AS-interface circuit)	
Protection class		IP20	
Resistance to shock		As per EN 61131-2	
Resistance to vibration		As per EN 61131-2	
Product weight	[g]	460	520
Dimensions W x L x H	[mm]	75 x 120 x 83	85 x 120 x 83
Materials			
Housing		High-alloy stainless steel	
Note on materials		Contains PWIS (paint-wetting impairment substances)	
		RoHS-compliant	

Technical data – Interfaces			
		CESA-GW-AS-PB	CESA-GW-AS-CO
Fieldbus interface			
Type		PROFIBUS to DIN 19245 Part 3	CANopen, Device Specification CiA DS-301
Connection technology		Sub-D socket, 9-pin	COMBICON plug, 5-pin
Transmission rate		9.6 kbps ... 12 Mbps	10 kbps ... 1 Mbps
Programming/diagnostic interface			
Type		RS 232 serial interface	

Operating and environmental conditions			
		CESA-GW-AS-PB	CESA-GW-AS-CO
Ambient temperature	[°C]	0 ... +55	
Storage temperature	[°C]	-25 ... +85	
Certification		cULus listed (OL)	
		C-Tick	
CE mark (see declaration of conformity) <sup>1)</sup>		To EU EMC Directive	


- 1) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: [www.festo.com/sp](http://www.festo.com/sp) → User documentation.  
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

# AS-interface® components

CESA AS-interface modules – Connections

FESTO

## Connection and display components



## Pin allocation – PROFIBUS


	Pin	Signal	Meaning
Sub-D socket to DIN 50170			
	1	n.c.	Not connected
	2	n.c.	Not connected
	3	RxD/TxD-P	Data transmission line B
	4	n.c.	Not connected
	5	DGND	Data reference potential (0 V)
	6	VP	Supply voltage (+5 V)
	7	n.c.	Not connected
	8	RxD/TxD-N	Data transmission line A
	9	n.c.	Not connected

## Pin allocation – CANopen

	Pin	Signal	Meaning
Terminal strip, 5-pin <sup>1)</sup>			
	1	V+	24 V DC supply CAN interface
	2	CAN_H	Received/transmitted data high
	3	Screened	Connection to FE (functional earth)
	4	CAN_L	Received/transmitted data low
	5	V-	0 V CAN interface

1) The interface is supplied with voltage via the plug.

## Pin allocation – AS-interface

		Signal	Meaning
Screw terminal			
	1	+AS-i-	Connection to AS-i circuit
	2	AS-i +PWR-	Supply voltage for AS-i circuit (max. 8 A)
	3	FE	Functional earth




### CESAAS-interface modules – Dimensions

**FESTO**


## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

CESA-GW-AS-PB



CESA-GW-AS-CO











Type	B1	B2	H1	H2	L1	L2
CESA-GW-AS-PB	76	7	125	120	75	55
CESA-GW-AS-CO	76	7	125	120	85	55

# AS-interface® components

CESA AS-interface modules – Accessories

**FESTO**

Ordering data				Part No.	Type
AS-interface gateway					
	AS-interface master with PROFIBUS DP fieldbus connection			567032	CESA-GW-AS-PB
	AS-interface master with CANopen fieldbus connection			567033	CESA-GW-AS-CO
PROFIBUS bus connection					
	Sub-D plug, angled			533780	FBS-SUB-9-WS-PB-K
AS-interface					
	AS-interface flat cable, yellow	100 m	18940	KASI-1,5-Y-100	
	AS-interface flat cable, black	100 m	18941	KASI-1,5-Z-100	
	Cable cap for flat cable (pack of 50)			18787	ASI-KK-FK
	Cable sleeve (pack of 20)			165593	ASI-KT-FK
	AS-interface module as bus termination			567035	CACF-BT-AS
	Primary switched mode, modular power supply 24 V DC power supply		5 A	2247681	CACN-3A-1-5
			10 A	2247682	CACN-3A-1-10
	H-rail to EN 60715			35430	NRH-35-2000



## Interface module CTEU-AS

The bus node manages communication between the valve terminal and a higher-order AS-Interface® master.

### General

The module has a system and load supply, a bus connection and a connection to the valve terminal with serial I-Port interface.

### Versions

The module has basic diagnostic functions. It has 3 integrated LEDs for on-site display.

A maximum of 2 byte inputs and 2 byte outputs are transmitted in the cyclic process image.

### Application


- Activation of up to 16 solenoid coils per valve terminal
- Automatic addressing
- Automatic detection of the number of connected valves

# AS-Interface® components

Bus node CTEU-AS

FESTO

## System overview




- Communication with the higher-order controller via fieldbus
- Use a bus node CTEU that is compatible with the fieldbus protocol
- Up to 24 valve positions (depending on the valve terminal)
- Flow rate of up to 1200 l/min (depending on the valve terminal)

## Connection of valve terminals to a higher-order I-Port master

### Overview

#### Valve terminal with I-Port interface

CTEU bus node  
(I-Port master)



#### Valve terminal

##### VTUG

- Up to 24 valve positions
- Flow rate of up to 1200 l/min

##### CPV

- Up to 8 valve positions
- Flow rate of up to 1200 l/min

##### VTUB-12

- Up to 35 valve positions
- Flow rate of up to 400 l/min

##### VTOC

- Up to 24 valve positions
- Flow rate of up to 10 l/min

##### MPA-L

- Up to 32 valve positions
- Flow rate of up to 870 l/min

# AS-Interface® components

Bus node CTEU-AS

FESTO

General technical data		
Fieldbus interface 1		
Protocol	AS-Interface	
Function	Bus connection incoming	
	Power supply	
Type	AS-Interface	
Connection type	Plug	
Connection technology	M12x1, A-coded to EN 61076-2-101	
Number of pins/wires	4	
Internal cycle time	[ms]	10
Fieldbus interface 2		
Function	Bus connection outgoing	
	Power supply	
Connection type	Socket	
Connection technology	M12x1, A-coded to EN 61076-2-101	
Number of pins/wires	4	
Inputs/outputs		
Max. address volume for inputs	[byte]	2
Max. address volume for outputs	[byte]	2

General data		
Device-specific diagnostics	System diagnostics	
	Undervoltage	
	Communication error	
Parameterisation	Watchdog enable	
	Watchdog disable	
Additional functions	Emergency message	
	Acyclic data access via SDO	
Configuration support	None	
Control components	DIL switch	
LED display	Product-specific	PS: Operating voltage for electronics and load supply
		X1: System status of module at I-Port 1
	Fieldbus-specific	AS-i: AS-Interface mode

Technical data – Electrical components		
Nominal operating voltage	[V DC]	30
Operating voltage range	[V DC]	20 ... 31.6
Intrinsic current consumption at nominal operating voltage	[mA]	Typically 50
Max. power supply	[A]	4


Technical data – Mechanical components		
Type of mounting	On electrical sub-base	
	On electrical interface	
Product weight	[g]	90 (without AS-i plug and without interlinking module)
Grid dimension	[mm]	40
Dimensions W x L x H	[mm]	40 x 91 x 50

Materials	
Housing	PA
Note on materials	RoHS-compliant
	Contains paint-wetting impairment substances

Operating and environmental conditions		
Ambient temperature	[°C]	–5 ... +50
Storage temperature	[°C]	–20 ... +70
Corrosion resistance class CRC <sup>1)</sup>		2
CE marking (see declaration of conformity) <sup>3)</sup>		To EU EMC Directive <sup>2)</sup>
Certification		c UL us - Listed (OL)
Degree of protection		IP65/IP67
Note on degree of protection		In assembled state
		Unused connections sealed

- 1) Corrosion resistance class CRC 2 to Festo standard FN 940070  
Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.
- 2) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: [www.festo.com/sp](http://www.festo.com/sp) → User documentation.  
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.
- 3) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.

Connection and display components



# AS-Interface® components

Bus node CTEU-AS – Connections



Pin allocation		
	Pin	Allocation
M12 plug connector, AS-Interface, incoming connection		
	1	AS-Interface +
	2	24 V load voltage supply
	3	AS-Interface –
	4	0 V load voltage supply
M12 socket, AS-interface, outgoing connection		
	1	AS-Interface +
	2	24 V load voltage supply
	3	AS-Interface –
	4	0 V load voltage supply

Dimensions				
CTEU-AS				











Type	B1	H1	H2	L1
CTEU-AS	91	45,3	39,7	40




# AS-Interface® components

Bus node CTEU-AS – Accessories

**FESTO**

Ordering data				
	Designation		Part No.	Type
Bus node				
	Bus node CTEU-AS (AS-Interface bus node)		<b>572555</b>	<b>CTEU-AS</b>
Bus connection				
	AS-interface flat cable, yellow	100 m	<b>18940</b>	<b>KASI-1,5-Y-100</b>
	AS-interface flat cable, black	100 m	<b>18941</b>	<b>KASI-1,5-Z-100</b>
	Cable cap for flat cable (pack of 50)		<b>18787</b>	<b>ASI-KK-FK</b>
	Cable sleeve (pack of 20)		<b>165593</b>	<b>ASI-KT-FK</b>
	Socket M12, 4-pin	For AS-interface flat cable	<b>18789</b>	<b>ASI-SD-PG-M12</b>
	M12 socket, 5-pin	For round cable	<b>18324</b>	<b>FBSD-GD-9-5POL</b>
Cable distributor				
	AS-Interface data to socket M12, 4-pin		<b>572225</b>	<b>NEFU-X22F-M12G4</b>
	AS-Interface data and load voltage supply to socket M12, 4-pin		<b>572226</b>	<b>NEFU-X24F-M12G4</b>
	AS-Interface data and load voltage supply to socket M12, 4-pin, cable length 1 m		<b>572227</b>	<b>NEFU-X24F-1-M12G4</b>
DUO plugs				
	Plug connector M12 for 2 connecting cables	4-pin, PG11	<b>18779</b>	<b>SEA-GS-11-DUO</b>
		5-pin, PG11	<b>192010</b>	<b>SEA-5GS-11-DUO</b>



## CPV valve terminals with AS-interface – Valve configuration options

CPV valve terminals with AS-interface can be configured with a wide range of valve slices. The system supports a maximum of 8 outputs and 8 inputs per AS-interface slave.

This gives the following basic valve slice configuration options (see tables on following page). Vacant positions can be configured instead of valve slices at any position.

### General data

- With or without 24 V DC auxiliary power supply for solenoid coils (EMERGENCY-STOP circuitry) depending on bus interface
- Solutions with and without integrated inputs
- Width 10, 14 or 18 mm

### Versions

- 2, 4 or 8 valve slices
- With 4 or 8 inputs, either
  - standard mode (SPEC V2.0)
  - A/B mode (SPEC V2.1)
  - A/B mode (SPEC V3.0, profile 7.A.7)
- Optionally with floating relay outputs
- Valves with integrated separation of channels 1 and 11
- Separator plates for the creation of pressure zones
- Suitable for vacuum
- Vacant positions for subsequent extension
- Optionally with pneumatic multiple connector plate

### Application

- Cost-effective connection of 2, 4 or 8 valve slices to the AS-interface
- Comprehensive range of valve functions
- Decentralised machine and system structures, for example
  - in handling technology
  - in conveyor technology
  - in the packaging industry
  - in sorting systems
  - in upstream machine functions



Note

Please follow the links below for more details on the various pneumatic functions.

- ➔ Info 213 Valve terminal CPV
- ➔ Internet: cpv

# AS-interface® components

CPV valve terminals

FESTO

Types of valve terminal with AS-interface									
Code	Type	Valve slices	Solenoid coils	Inputs (M8 connection)	Auxiliary power supply		Size		
					With	Without	CPV10	CPV14	CPV18
AZ	CPV1x-GE-ASI-2-Z	2	4	—	■	—	■	■	■
AZ	CPV18-GE-ASI-4-Z	4	4	—	■	—	—	—	■
AE/AO	CPV1x-GE-ASI-4E4A (-Z)	4	4	4	■	■	■	■	—
AE	CPV1x-GE-ASI-8E8A-Z	8	8	8	■	—	■	■	—
BE	CPV1x-GE-ASI-4E3A (-Z)	4	3	4	■	—	■	■	—
BE	CPV1x-GE-ASI-8E6A-Z	8	6	8	■	—	■	■	—
CE	CPV1x-GE-ASI-4E4A-Z-M8-CE	4	4	4	■	—	■	■	—
CE	CPV1x-GE-ASI-8E8A-Z-M8-CE	8	8	8	■	—	■	■	—

1) The load voltage (auxiliary power supply via the black cable) can be connected/disconnected separately.


Permissible combinations in valve position allocation								
Type	Slave n				Slave n+1			
	0	1	2	3	4	5	6	7
CPV1x-GE-ASI-2-Z	M	M						
	J	M						
	M	J						
	J	J						
CPV18-GE-ASI-4-Z	M	M	M	M				
CPV1x-GE-ASI-4E4A (-Z)	M	M	M	M				
CPV10-GE-ASI-4A (-Z)	J	Vacant position	M	M				
CPV14-GE-ASI-4A (-Z)	M	M	J	Vacant position				
	J	Vacant position	J	Vacant position				
CPV1x-GE-ASI-4E3A -Z <sup>1)</sup>	M	M	M	Vacant position				
	J	Vacant position	M	Vacant position				
CPV1x-GE-ASI-8E8A-Z <sup>1)</sup>	M	M	M	M	M	M	M	M
CPV1x-GE-ASI-8E8A-Z-CE <sup>1)</sup>	J	Vacant position	M	M	M	M	M	M
	M	M	J	Vacant position	M	M	M	M
	J	Vacant position	J	Vacant position	M	M	M	M
	...	...	...	...	...	...	...	...
	M	M	M	M	J	Vacant position	M	M
	M	M	M	M	M	M	J	Vacant position
	M	M	M	M	J	Vacant position	J	Vacant position
CPV1x-GE-ASI-8E6A-Z <sup>1)</sup>	M	M	M	Vacant position	M	M	M	Vacant position
	M	M	M	Vacant position	J	Vacant position	M	Vacant position
	J	Vacant position	M	Vacant position	M	M	M	Vacant position
	J	Vacant position	M	Vacant position	J	Vacant position	M	Vacant position

- 1) - Valve slices with 2 outputs must be configured at positions 0, 2, 4, 6 (or positions 0, 4 with A/B mode).  
 - Valve slices with 2 outputs always have a vacant position.  
 - Slaves n and n+1 can be configured independently of one another. This gives a total of 16 different configuration options.
- M Valve slice with single solenoid valve or a different valve slice with an output.  
 J Valve slice with double solenoid valve or a different valve slice with two outputs.

## AS-interface® components

CPV valve terminals with integrated inputs, to SPEC V2.0

FESTO



### CPV valve terminals with integrated inputs, to Specification V2.0

#### General data

- Cubic design for exceptional performance and low weight
- Highly flexible thanks to various pneumatic functions (valve variants), different pressure ranges, vacuum switches and the option of integrated vacuum generation
- Floating relay outputs (optional)
- Connection for auxiliary power supply for EMERGENCY-STOP conditions
- Protection class IP65

#### LED displays for:

- Status display for inputs
- Switching status of valves
- PWR-LED (power)
- FAULT-LED (fault)

#### Versions

- Width 10 and 14 mm
- 4 or 8 inputs
- 4 or 8 valve positions
- Up to four pressure zones
- Suitable for vacuum
- Vacuum generation

- Various valve functions on one valve terminal, for example
  - 2x 3/2-way valve
  - 5/2-way valve, single solenoid
  - 5/2-way valve, double solenoid
  - 5/3-way valve
  - 2x 2/2-way valve
  - Valves with integrated separation of channels 1 and 11
  - Separator plate
  - Vacant position
- Additional function (screwed onto valve slice)
  - One-way flow control valve
- Various mounting options

#### Application

- Flexible and cost-effective connection of 4 or 8 valve slices and up to 8 sensors to the M8 inputs to Spec. V2.0, 31 slaves, bus cycle max. 5 ms. Executable on all masters from Spec. V2.0 or higher.



Note

Please follow the links below for more details on the various pneumatic functions.

- ➔ Info 213 Valve terminal CPV
- ➔ Internet: cpv

# AS-interface® components

CPV valve terminals with integrated inputs, to SPEC V2.0


FESTO

Technical data				
Type		CPV-...-GE-ASI-4E4A-Z-M8	CPV-...-GE-ASI-4E4A-M8	CPV-...-GE-ASI-8E8A-Z-M8
Part No.	Order via order code/valve terminal configurator			
Code	AE			
Valves	Number of valve slices/coils	4	4	8
	Valve width [mm]	10/14		
	Setting of the valve configuration	Integrated DIL switch		
	External power supply 24 V DC	Yes	No	Yes
	Digital inputs	4	4	8
	Connection technology	M8, 3-pin		
	Sensor supply via AS-interface	Short circuit and overload proof		
	Sensor connection	2-wire and 3-wire sensors		
	Type	IEC 1131-2, type 2		
	Input circuitry	PNP (positive switching)		
AS-interface connection	Connection technology	AS-interface flat cable plug (included in scope of delivery)		
	Voltage range [V DC]	26.5 ... 31.6, reverse polarity protected		
	Residual ripple [mVss]	20		
	Current consumption [mA]		CPV10/14	
	of inputs			
	• In 0 status	7	61/95	40
	• In 1 status (no current consumption by sensors)	35	89/123	96
	• In 1 status (max. current consumption by sensors)	240	191/225	278
	• Max. per input	200	200	200
	• Max. per valve			
	– when switching on		25/38.75	
	– following a current reduction		8.75/12.5	
Load voltage connection	Connection technology	AS-interface flat cable plug (version turned through 180° must be ordered separately)		
	Nominal voltage [V DC]	24 ±10%		
	Residual ripple [Vss]	4		
	Current consumption of valves	CPV10/14	No load voltage connection	CPV10/14
	• when switching on [mA]	108/176		200/310
	• following a current reduction [mA]	42/72		70/100
LED displays	ASI-LED	Power/green		
	AUX-PWR-LED	Auxiliary power supply/green	None	Auxiliary power supply/green
	FAULT-LED	Fault LED/red		
	Inputs	Green		
	Valves	Yellow		
General data	Protection class (to EN 60529)	IP65 (fully assembled)		
	Electromagnetic compatibility			
	• Interference emission	Tested to EN 55011, limit value class B		
	• Interference immunity	Tested to DIN EN 61000-4-2, DIN EN 61000-4-4 and EN V 50140		
	CE mark	Yes, in accordance with EU Directive 89/336/EEC		
	Temperature range [°C]	Operation: –5 ... +50; storage/transport: –20 ... +70		
	Materials	Housing: aluminium; cover: polyamide; seals: nitrile rubber; polychloroprene rubber		
	Dimensions	➔ 33		
	Weight	➔ 33		
	Pneumatic data	➔ Info 213 Valve terminal CPV		
		➔ Internet: cpv		
AS-interface data	ID code	F <sub>H</sub> (ID = F <sub>H</sub> ; ID1 = F <sub>H</sub> ; ID2 = F <sub>H</sub> )		
	IO code	7 <sub>H</sub>		
	Profile	S-7.F		

# AS-interface® components

FESTO

CPV valve terminals with integrated inputs, for A/B mode to SPEC V2.1



## CPV valve terminals with integrated inputs, for A/B mode to Specification V2.1<sup>1)</sup>

### General data

- A/B mode increases the performance of each master
  - 100% more inputs (248 instead of 124)
  - 50% more outputs (186 instead of 124)
- Cubic design for exceptional performance and low weight
- Highly flexible thanks to various pneumatic functions (valve variants), different pressure ranges, vacuum switches and the option of integrated vacuum generation
- Floating relay outputs, optional

- Connection for auxiliary power supply for EMERGENCY-STOP conditions
- Protection class IP65

### LED displays for:

- Status display for inputs
- Switching status displays for valves
- PWR-LED (power)
- FAULT-LED (fault)<sup>2)</sup>

### Versions

- Width 10 and 14 mm
- 4 or 8 inputs
- 3 or 6 valve positions

- Up to four pressure zones
- Suitable for vacuum
- Vacuum generation
- Various valve functions on one valve terminal, for example
  - 2x 3/2-way valve
  - 5/2-way valve, single solenoid
  - 5/2-way valve, double solenoid
  - 5/3-way valve
  - 2x 2/2-way valve
  - Valves with integrated separation of channels 1 and 11
  - Separator plate
  - Vacant position

- Additional function (screwed onto valve slice)
  - One-way flow control valve
- Various mounting options

### Application

- AS-i networks with A/B mode to SPEC V2.1 and SPEC V3.0, 62 slaves, bus cycle 10 ms
- Flexible and cost-effective connection of 3 or 6 valve slices and up to 8 sensors to the M8 inputs

1) Slave compatible with SPEC V3.0

2) Peripherals faults to SPEC V2.1 not yet implemented



Note

Please follow the links below for more details on the various pneumatic functions.

➔ Info 213 Valve terminal CPV

➔ Internet: cpv

# AS-interface® components

CPV valve terminals with integrated inputs, for A/B mode to SPEC V2.1

FESTO


Technical data				
Type		CPV-...-GE-ASI-4E3A-Z-M8		CPV-...-GE-ASI-8E6A-Z-M8
Part No.		Order via order code/valve terminal configurator		
Code		BE		BE
Valves	Number of valve slices/coils		3	
	Valve width [mm]		10/14	
	Setting of the valve configuration		Integrated DIL switch	
	External power supply 24 V DC		Yes	
	Digital inputs		4	8
	Connection technology		M8, 3-pin	
	Sensor supply via AS-interface		Short circuit and overload proof	
	Sensor connection		2-wire and 3-wire sensors	
	Type		IEC 1131-2, type 2	
	Input circuitry		PNP (positive switching)	
AS-interface connection	Connection technology		AS-interface flat cable plug (included in scope of delivery)	
	Voltage range [V DC]		26.5 ... 31.6, reverse polarity protected	
	Residual ripple [mVss]		20	
	Current consumption of inputs [mA]			
	• In 0 status		7	40
	• In 1 status (no current consumption by sensors)		35	96
	• In 1 status (max. current consumption by sensors)		137	278
Load voltage connection	Connection technology		AS-interface flat cable plug (version turned through 180° must be ordered separately)	
	Nominal voltage [V DC]		24 ±10%	
	Residual ripple [Vss]		4	
	Current consumption of valves		CPV10/14	CPV10/14
	• when switching on [mA]		81/132	150/233
	• following a current reduction [mA]		32/54	53/75
LED displays	ASI-LED		Power/green	
	AUX-PWR-LED		Auxiliary power supply/green	
	FAULT-LED		Fault LED/red	
	Inputs		Green	
	Valves		Yellow	
General data	Protection class (to EN 60529)		IP65 (fully assembled)	
	Electromagnetic compatibility			
	• Interference emission		Tested to EN 55011, limit value class B	
	• Interference immunity		Tested to DIN EN 61000-4-2, DIN EN 61000-4-4 and EN V 50140	
	CE mark		Yes, in accordance with EU Directive 89/336/EEC	
	Temperature range [°C]		Operation: -5 ... +50; storage/transport: -20 ... +70	
	Materials		Housing: aluminium; cover: polyamide; seals: nitrile rubber, polychloroprene rubber	
	Dimensions		➔ 33	
	Weight		➔ 33	
	Pneumatic data		➔ Info 213 Valve terminal CPV	
AS-interface data	ID code		ID = A <sub>H</sub> ; ID1 = 7 <sub>H</sub> ; ID2 = E <sub>H</sub>	
	IO code		7 <sub>H</sub>	
	Profile		S-7.A.E	



# AS-interface® components

FESTO

CPV valve terminals with integrated inputs, for A/B mode to SPEC V3.0



## CPV valve terminals with integrated inputs, for A/B mode to specification V3.0, profile 7.A.7

### General data

- A/B mode increases the performance of each master
  - 100% more inputs (248 instead of 124)
  - 100% more outputs (248 instead of 124)
- Cubic design for exceptional performance and low weight
- Highly flexible thanks to various pneumatic functions (valve variants), different pressure ranges, vacuum switches and the option of integrated vacuum generation
- Floating relay outputs, optional

- Connection for auxiliary power supply for EMERGENCY-STOP conditions
- Protection class IP65

### LED displays for:

- Status display for inputs
- Switching status displays for valves
- PWR-LED (power)
- FAULT-LED (fault)

### Versions

- Width 10 and 14 mm
- 4 or 8 inputs
- 4 or 8 valve positions

- Up to four pressure zones
- Suitable for vacuum
- Vacuum generation
- Various valve functions on one valve terminal, for example
  - 2x 3/2-way valve
  - 5/2-way valve, single solenoid
  - 5/2-way valve, double solenoid
  - 5/3-way valve
  - 2x 2/2-way valve
  - Valves with integrated separation of channels 1 and 11
  - Separator plate
  - Vacant position

- Additional function (screwed onto valve slice)
  - One-way flow control valve
- Various mounting options

### Application

- AS-i networks with A/B mode to SPEC V3.0, profile 7.A.7, 62 slaves, bus cycle 20 ms
- Flexible and cost-effective connection of 4 or 8 valve slices and up to 8 sensors to the M8 inputs



Note  
Slaves to Specification V3.0 require an ASi master to Specification V3.0; these detect the new slave profiles automatically.

Please follow the links below for more details on the various pneumatic functions.  
➔ Internet: [cpv](http://cpv)



# AS-interface® components

CPV valve terminals with integrated inputs, for A/B mode to SPEC V3.0


FESTO

Technical data			
Type		CPV-...-GE-ASI-4E4A-Z M8-CE	CPV-...-GE-ASI-8E8A-Z M8-CE
Part No.	Order via order code/valve terminal configurator		
Code	CE		CE
Valves	Number of valve slices/coils	4	8
	Valve width [mm]	10/14	
	Setting of the valve configuration	Integrated DIL switch	
	External power supply [V DC]	24	
	Digital inputs	4	8
	Connection technology	M8, 3-pin	
	Device-specific diagnostics	Short circuit/overload of inputs	
	Sensor connection	2-wire and 3-wire sensors	
	Input characteristic	IEC 1131-2, type 2	
	Switching logic at inputs	PNP (positive switching)	
AS-interface connection	Connection technology	AS-interface flat cable plug (included in scope of delivery)	
	Number of slaves per device	1	2
	Voltage range [V DC]	26.5 ... 31.6, reverse polarity protected	
	Residual ripple [mVss]	20	
	Debounce time at inputs (at 24 V) [ms]	Typically 3	
	Set using AS-interface addressing device	1A ... 31A (0) 1B ... 31B	
	Switching level [V]		
	Signal 0	≤ 5	
	Signal 1	≥ 11	
	Current consumption of inputs [mA]		
	• In 0 status	20	40
	• In 1 status (no current consumption by sensors)	Max. 48	Max. 96
	• Max. per input	200	200
Load voltage connection	Connection technology	AS-interface flat cable plug (version turned through 180° must be ordered separately)	
	Nominal voltage [V DC]	24 ±10%	
	Residual ripple [Vss]	4	
	Current consumption of valves (type-dependent)	CPV10/14	CPV10/14
	• when switching on [mA]	Max. 115/175	Max. 240/460
	• following a current reduction [mA]	Max. 55/75	Max. 95/120
LED displays	ASI-LED	Power/green	
	AUX-PWR-LED	Auxiliary power supply/green	
	FAULT-LED	Fault LED/red	
	Inputs	Green	
	Valves	Yellow	
General data	Protection class (to EN 60529)	IP65 (fully assembled)	
	Relative air humidity [%]	0 ... 95 (non-condensing)	
	CE mark	To EU EMC Directive	
	Temperature range [°C]	Operation: -5 ... +50; storage/transport: -20 ... +70	
	Materials	Housing: aluminium die-cast; cover: polyamide; seals: nitrile rubber, polychloroprene rubber	
	Dimensions	➔ 33	
	Weight	➔ 33	
	Pneumatic data	➔ Internet: cpv	
AS-interface data	ID code	ID = A <sub>H</sub> ; ID1 = 7 <sub>H</sub> ; ID2 = 7 <sub>H</sub>	
	IO code	7 <sub>H</sub>	
	Profile	S-7.A.7	

## AS-interface® components

CPV valve terminals without inputs, to SPEC V2.1

FESTO



### CPV valve terminals without inputs, to Specification V2.1<sup>1)</sup>

#### General data

- Cubic design for exceptional performance and low weight
- Highly flexible thanks to various pneumatic functions (valve variants), different pressure ranges, vacuum switches and the option of integrated vacuum generation
- Floating relay outputs, optional
- Connection for auxiliary power supply for EMERGENCY-STOP conditions
- Protection class IP65

#### LED displays for:

- Switching status displays for valves
- PWR-LED (power)
- FAULT-LED (fault)<sup>2)</sup>
- Valve diagnostics: short circuit or wire break at valve solenoid coil, valve does not respond (no movement of the plunger)

#### Versions

- Width 10, 14 and 18 mm
- 2 or 4 valve positions
- Up to two pressure zones
- Suitable for vacuum
- Vacuum generation

- Valve terminal with 4 valve positions:
  - With or without 24 V DC auxiliary power supply for solenoid coils (EMERGENCY-STOP circuitry)
  - The auxiliary power supply is always integrated and can be subsequently switched off using the DIL switch
- Various valve functions on one valve terminal, for example
  - 2x 3/2-way valve
  - 5/2-way valve, single solenoid
  - 5/2-way valve, double solenoid
  - 5/3-way valve

- 2x 2/2-way valve
- Valves with integrated separation of channels 1 and 11
- Separator plate
- Vacant position
- Additional function (screwed onto valve slice)
  - One-way flow control valve
- Extensive mounting options

#### Application

- Flexible and cost-effective connection of 2 or 4 valve slices, 31 slaves, bus cycle max. 5 ms



Note

Please follow the links below for more details on the various pneumatic functions.

➔ Internet: cpv

1) Slave compatible with SPEC V3.0

2) Valve terminal with 4 valve positions: peripherals faults to SPEC V2.1 implemented  
Valve terminal with 2 valve positions: peripherals faults not implemented

# AS-interface® components

CPV valve terminals without inputs, to SPEC V2.1

FESTO

Technical data				
Type			CPV—...-GE-ASI-2-Z	CPV—...-GE-ASI-4-Z <sup>1)</sup>
Part No.			Order via order code/valve terminal configurator	
Code			AZ	AS/AZ
Valves	Number of valve slices/coils		2/4	4/4
	Valve width	10 mm	■	■
		14 mm	■	■
		18 mm	■	■
	Setting of the valve configuration		None (permanently assigned)	CPV 10/14 Integrated DIL switch, CPV 18 <sup>3)</sup>
	External power supply 24 V DC		Yes	Yes <sup>2)</sup> Set using DIL switch
AS-interface connection	Connection technology		AS-interface flat cable plug (must be ordered separately)	
	Voltage range	[V DC]	26.5 ... 31.6, reverse polarity protected	
	Residual ripple	[mVss]	20	
	Current consumption of all valves		CPV10/14/18	CPV10/14/18
	• without current reduction	[mA]	25/25/25	25/25/25
	• with current reduction	[mA]	25/25/25	25/25/25
Load voltage connection	Connection technology		AS-interface flat cable plug (must be ordered separately)	
				Blanking plug for sealing the unused connection enclosed
	Nominal voltage	[V DC]	24 ±10%	
	Residual ripple	[Vss]	4	
	Max. starting current		CPV10/14/18	CPV10/14/18
	• before current reduction	[mA]	108/176/320	110/165/246
	• following a current reduction	[mA]	48/72/120	35/40/100
LED displays	PWR-LED		Power/green	
	FAULT-LED		Fault LED/red	Peripherals fault LED/red Valve diagnostics: short circuit or wire break at valve solenoid coil, valve does not respond (no movement of the plunger)
	Valves		Yellow	
General data	Protection class (to EN 60 529)		IP65 (fully assembled)	
	Electromagnetic compatibility			
	• Interference emission		Tested to EN 55011, limit value class B	
	• Interference immunity		Tested to DIN EN 61000-4-2, DIN EN 61000-4-4 and EN V 50140	
	CE mark		Yes, in accordance with EU Directive 89/336/EEC	
	Temperature range	[°C]	Operation: –5 ... +50; storage/transport: –20 ... +70	
	Materials		Housing: aluminium die-cast; cover: polyamide; seals: nitrile rubber, polychloroprene rubber	
	Dimensions		➔ 33	
	Weight		➔ 33	
Pneumatic data		➔ Internet: cpv		
AS-interface data	ID code		F <sub>H</sub>	
	IO code		8 <sub>H</sub>	
	ID2 code		F <sub>H</sub>	E <sub>H</sub> (F <sub>H</sub> with CPV18)
	Profile		S-8.F	S-8.F.E
	Parameter P3 CPV valve diagnostic function			1 = enable 2 = disable
	Default		1 for CPV with valve diagnostics	

1) New as of hardware status 0105: single or double solenoid valves can be configured by means of a DIL switch.

2) With or without 24 V DC auxiliary power supply for solenoid coils (EMERGENCY-STOP circuitry). The auxiliary power supply is always integrated and can be switched on/off using the DIL switch.

3) None (permanently assigned)


# AS-interface® components

CPV valve terminals – Connections/displays




## Overview of connections/displays – CPV with AS-interface

CPV-...-GE-ASI-2-Z / ASI-4-(Z)




- 1 AS-interface bus connection
- 2 PWR LED (power, green)  
Fault LED (fault, red)
- 3 Auxiliary power supply for valves (optional)
- 4 Inscription areas
- 5 LED display for valves

## CPV-...-GE-ASI-4E4A-(Z) / 4E/3A-...- / 4E/4A-...-CE



- 1 AS-interface bus connection
- 2 PWR LED (power, green)  
Fault LED (fault, red)
- 3 Auxiliary power supply for valves (optional)
- 4 LED display for inputs (green)
- 5 Sensor connections
- 6 Inscription areas
- 7 LED display for valves (yellow)

## CPV-...-GE-ASI-8E8A-Z / 8E/6A / 8E/8A-...-CE



- 1 AS-interface bus connection
- 2 PWR LED (power, green)  
Fault LED (fault, red)
- 3 Auxiliary power supply for valves (optional)
- 4 LED display for inputs (green)
- 5 Address selector button with LED
- 6 Sensor connections
- 7 Inscription areas
- 8 LED display for valves (yellow)

Pin allocation		
Inputs CPV	Pin	Allocation
	1	+24 V
	3	0 V
	4	Input

# AS-interface® components

CPV valve terminals – Weights/dimensions


FESTO

Weights [g] – Valve terminal CPV with AS-interface			
Type	CPV10	CPV14	CPV18
Electrical connection plate with AS-interface connection			
• with 2 valve positions	85	130	275
• with 4(3) valve positions	110	175	355
• with 8(6) valve positions	200	300	
End plate, 2 pieces	160	280	740
Pneumatic multiple connector plate			
• on CP valve terminal with 2 valve positions	120	270	520
• on CP valve terminal with 4 valve positions	165	390	750
• on CP valve terminal with 6 valve positions	225	510	870
• on CP valve terminal with 8 valve positions	270	630	1300
Flat plate silencer	147	234	–
Relay plate	35	55	–
Blanking plate	25	45	90
Separator plate	25	45	90
Valve plate/vacuum generator	65	110	260
Functional module: One-way flow control valves	25	54	125

## Dimensions – CPV with AS-interface

Download CAD data → [www.festo.com](http://www.festo.com)

Without integrated inputs




- 1 Slots for inscription labels
- 2 Pneumatic multiple connector plate
- 3 Inscription label holder

		L1	L2	L3	L4	L5	L6	L7	L12	L14	L15	L16	L17
CPV10	2-fold	50	41.8	62	71	52.8	15	9.5	–	10.9	38.1	2.5	35.5
	4-fold	70	61.8	62	71	52.8	15	9.5	23.5	10.9	38.1	2.5	35.5
CPV14	2-fold	68	58	78	89	58.8	20	9.5	–	14	52	5	35.5
	4-fold	96	86	78	89	58.8	20	9.5	23.5	14	52	5	35.5
CPV18	2-fold	96	85.5	106.5	118	73	20	9.5	–	27.4	68.2	10.4	40
	4-fold	132	121.5	106.5	118	73	20	9.5	28	27.4	68.2	10.4	40


Dimensions – CPV with AS-interface

CPV10/14 with integrated inputs



Download CAD data → [www.festo.com](http://www.festo.com)

CPV10 with integrated inputs




		L1	L2	L3	L4	L5	L6	L7	L18	L19	L20	L21
CPV10	4-fold	70	61.8	62	71	52.8	15	9.5	10.9	38.1	35	3
	8-fold	110	101.8						10.4	38.6	31.9	
CPV14	4-fold	96	86	78	89	58.8	20	9.5	18.8	46.8	43.3	5

Dimensions – CPV with AS-interface

Download CAD data → [www.festo.com](http://www.festo.com)

CPV14 with integrated inputs















- 1 Slots for inscription labels
- 2 Pneumatic multiple connector plate
- 3 Inscription label holder (CPV14-VI-BZ-T-... or CPV14-VI-ST-T-...)

		L1	L2	L3	L4	L5	L6	L7	L18	L19	L20	L21
CPV14	8-fold	152	142	78	89	58.8	20	9.5	18.8	46.8	46.3	5

# AS-interface® components

CPV valve terminals – Accessories

**FESTO**










Ordering data				
	Description		Part No.	Type
Bus connection				
	AS-interface flat cable, yellow	100 m	18940	KASI-1,5-Y-100
	AS-interface flat cable, black	100 m	18941	KASI-1,5-Z-100
	Flat cable socket		18785	ASI-SD-FK
	Flat cable socket	Turned through 180°	196089	ASI-SD-FK180
	Flat cable blanking plug		196090	ASI-SD-FK-BL
	AS-interface flat cable distributor	Parallel cable	18786	ASI-KVT-FK
	AS-interface flat cable distributor	Symmetrical cable	18797	ASI-KVT-FK-S
	Cable cap for flat cable (scope of delivery 50 pieces)		18787	ASI-KK-FK
	Cable sleeve (scope of delivery 20 pieces)		165593	ASI-KT-FK
Sensor plugs				
	Straight sensor plug	M8, screw-in, 3-pin	192009	SEA-3GS-M8-S
	Straight sensor plug	M8, solderable, 3-pin	18696	SEA-GS-M8
	Cover cap (scope of delivery 10 pieces)	M8	177672	ISK-M8
Connecting cable				
	Modular system for connecting cables ➔ Internet: nebu		–	NEBU-...
	Straight plug M8, 3-pin, straight socket M8, 3-pin	0.5 m	541346	NEBU-M8G3-K-0.5-M8G3
		1.0 m	541347	NEBU-M8G3-K-1-M8G3
		2.5 m	541348	NEBU-M8G3-K-2.5-M8G3
		5.0 m	541349	NEBU-M8G3-K-5-M8G3



# AS-interface® components

CPV valve terminals – Accessories

**FESTO**

Ordering data				
	Description		Part No.	Type
Miscellaneous				
	Primary switched mode, modular power supply 24 V DC power supply	5 A	2247681	CACN-3A-1-5
		10 A	2247682	CACN-3A-1-10
	Addressing device (power supply plug included in scope of delivery)		18959	ASI-PRG-ADR
	Addressing cable		18960	KASI-ADR
	AS-interface input module for 8 inputs M8		542124	ASI-8DI-M8-3POL
	AS-interface input/output module for 4 inputs/3 outputs M12		542125	ASI-4DI3DO-M12X2-5POL-Z
	Inscription labels 6x10mm in frames (64pieces)		18576	IBS 6x10
	Inscription labels 9x20mm in frames (20 pieces)		18182	IBS 9x20
	H-rail to EN 60715		35430	NRH-35-2000
	Mounting for H-rail		162556	CPV10/14-VI-BG-NRH-35
			163291	CPV18-VI-BG-NRH-35
User's manual				
	CPV Pneumatics Description	German	165100	P.BE-CPV-DE
		English	165200	P.BE-CPV-EN
		French	165130	P.BE-CPV-FR
		Italian	165160	P.BE-CPV-IT
		Spanish	165230	P.BE-CPV-ES



## MPA-S valve terminals with AS-interface – Valve configuration options

MPA valve terminals with AS-interface can be flexibly configured with a wide range of valves. The system supports a maximum of 8 outputs (solenoid coils) and 8 inputs per valve terminal. This gives the following basic valve configuration options (see tables on following page).

-  - Note

Please follow the link below for more details on the various pneumatic functions.

➔ Internet: mpa-s

### General data

- Solutions with integrated inputs
- Width 10, 14 or 20 mm
- With or without 24 V DC auxiliary power supply for solenoid coils (EMERGENCY-STOP circuitry) in the case of the 4I/4O version. The auxiliary power supply is always integrated in the version with 8 inputs and cannot be subsequently switched off using the DIL switch
- Selectable bus connection technology
  - Flat cable for AS-interface with 4I/4O version
  - 4-pin M12 round plug<sup>1)</sup> with 4I/4O and 8I/8O version
- Selectable addressing
  - Via bus connection (M12 or flat cable)

### Versions

- 2 to 8 valves, freely configurable
- With 4 or 8 inputs
- M12, M8, quick connection, tension spring or Sub-D connection technology
- Separating seals for the creation of pressure zones
- Suitable for vacuum
- Subsequent extensions either
  - via unused valve positions
  - by converting the valve terminal

### Application

- Flexible and cost-effective connection of 2 or 8 valves (max. 8 solenoid coils) with input feedback
- Decentralised machine and system structures, for example
  - in handling technology
  - in conveyor technology
  - in the packaging industry
  - in sorting systems
  - suitable for energy chains thanks to connection via round cables

1) Suitable cable distributor from flat cable to M12 ➔ 49

➔ Info 214 Valve terminal CPA

# AS-interface® components

MPA-S valve terminal – Connection technology and addressing

FESTO

Types of valve terminal with AS-interface										
Type	Valves	Solenoid coils	Inputs	Conforms to SPEC	Extended addressing range	Auxiliary power supply can be disconnected		Width		
						Yes	No	10 mm	14 mm	20 mm
VMPA-ASI-EPL-E-4E4A-Z	4	4	4	2.1	–	■	–	■	■	■
VMPA-ASI-EPL-G-4E4A-Z	4	4	4	2.1	–	■	–	■	■	■
VMPA-ASI-EPL-EU-4E4A-Z	4	4	4	2.1	–	■	–	■	■	■
VMPA-ASI-EPL-GU-4E4A-Z	4	4	4	2.1	–	■	–	■	■	■
VMPA-ASI-EPL-E-8E8A-Z	8	8	8	2.1	–	–	■	■	■	■
VMPA-ASI-EPL-G-8E8A-Z	8	8	8	2.1	–	–	■	■	■	■
VMPA-ASI-EPL-EU-8E8A-Z	8	8	8	2.1	–	–	■	■	■	■
VMPA-ASI-EPL-GU-8E8A-Z	8	8	8	2.1	–	–	■	■	■	■
VMPA-ASI-EPL-E-8E8A-CE	8	8	8	3.0	■	–	■	■	■	■
VMPA-ASI-EPL-G-8E8A-CE	8	8	8	3.0	■	–	■	■	■	■
VMPA-ASI-EPL-EU-8E8A-CE	8	8	8	3.0	■	–	■	■	■	■
VMPA-ASI-EPL-GU-8E8A-CE	8	8	8	3.0	■	–	■	■	■	■

Permissible combinations in valve position allocation				
Type	Slave n			
	0	1	2	3
4I/4O MPA1 and MPA14 – only M (up to 4 valves per sub-base)	M	M	M	M
	M	M	M	L
	M	M	L	L
	M	L	L	L
4I/4O MPA2 (2 valves per sub-base)	M	M	M	M
	J	M	–	–
	M	J	–	–
	J	J	–	–

- 1) All valve slices can be freely configured (up to the maximum number of valve solenoids supported (4 or 8).  
A blanking plate can be used instead of the valve slice as a vacant position for one or two solenoid coils.
- M Valve slice with single solenoid valve or a different valve slice with an output.  
J Valve slice with double solenoid valve or a different valve slice with two outputs.  
L Vacant position

# AS-interface® components



MPA-S valve terminal – Connection technology and addressing

Permissible combinations in valve position allocation								
Type	Slave n plus slave n+1							
	0	1	2	3	4	5	6	7
8I/8O MPA1 and MPA14 (up to 4 valves per sub-base)	M	M	M	M	M	M	M	M
	M	M	M	L	M	M	M	L
	J	J	J	J	–	–	–	–
	...	...	...	...	...	...	...	...
	J	J	J	J	–	–	–	–
	J	J	J	M	–	–	–	–
	J	J	M	M	–	–	–	–
	...	...	...	...	...	...	...	...
	J	J	L	L	–	–	–	–
8I/8O MPA2 (2 valves per sub-base)	M	M	M	M	M	M	M	M
	M	M	M	L	M	M	M	L
	...	...	...	...	...	...	...	...
	J	J	J	J	–	–	–	–
	J	J	J	M	–	–	–	–
	J	J	M	M	–	–	–	–
	...	...	...	...	...	...	...	...
	J	J	M	M	M	M	–	–
	J	J	M	M	M	L	–	–
	...	...	...	...	...	...	...	...
	M	M	M	M	J	J	–	–

- 1) All valve slices can be freely configured (up to the maximum number of valve solenoids supported (4 or 8).  
A blanking plate can be used instead of the valve slice as a vacant position for one or two solenoid coils.
- M Valve slice with single solenoid valve or a different valve slice with an output.  
J Valve slice with double solenoid valve or a different valve slice with two outputs.  
L Vacant position


# AS-interface® components

MPA-S valve terminal – Connection technology and addressing


FESTO

## Installation: Selectable connection technology for AS-interface

### Support for flat cables




- Straightforward cabling with flat cables in protected areas
- Fast system of installation with standard AS-interface cables
- Standard installation at the AS-interface with yellow flat cables is possible with the 4I/40 MPA-S version




Standard installation at the AS-interface flat cable

### Support for round cables



Local round cable wiring system for areas subjected to consistently high stress:


- Permanently high humidity
- Need for flexible cabling using one cable
- Use in energy chains with highly flexible cables



- 1 Pre-assembled M12 round cable, 1 m, polyurethane
- 2 Selectable cable for additional slave, for example highly flexible cable for energy chains or PVC cable for applications requiring resistance to detergents

## Addressing


### Addressing device



The addressing device to SPEC V2.1 can be used to scan the AS-interface from any point in the network. At all connected stations

- slave addresses can be read/changed
- ID and IO codes can be read out
- parameters can be read/changed
- input/output data can be read and written (setting outputs)
- error messages can be read out and quickly recognised

### AS-interface connections




- 1 M12 plug for AS-interface and incoming auxiliary supply
- 2 M12 socket for AS-interface and outgoing auxiliary supply

# AS-interface® components

MPA-S valve terminal – Connection technology and addressing

FESTO

## AS-interface flat cable distributor to round cable



### Alternative connection concepts

- AS-interface connection technology for yellow and optionally for black flat cables
- Passive conversion of the signals to M12 socket and round cable via M12 socket
- Pre-assembled round cable, PUR, 1 m long
- Alternatively PVC extension cable, 2.5 and 5 m, via additional M12 socket

### Selecting the cable

Optimised connection technologies at the AS-interface can be easily realised by selecting the right cable.


- Flat cables for all standard applications with installation-saving insulation displacement technology
- Round cables for applications with differing requirements, for example:
  - Energy chains with small radii and further requirements for highly flexible cables

- Applications with consistently high humidity
- Applications involving frequent cleaning and requiring cables resistant to detergents (PUR, PVC or other cables)
- Cabling systems using standard components (M12) preferred

### Easy to mount

- Direct mounting on a wall or machine frame

## Supplementary compact I/O modules



The valve terminals MPA-S can be supplemented with the compact I/O modules. The following are available:

- 8 inputs M8
- 4 inputs/3 outputs M12

# AS-interface® components

Key features – Display and operation

FESTO

## Display and operation

Each valve solenoid coil is allocated an LED which indicates its signal status.

- Indicator 12 shows the switching status of the coil for output 2
- Indicator 14 shows the switching status of the coil for output 4

### Manual override

The manual override (MO) enables the valve to be actuated when not electrically activated or energised. The valve is activated by pushing the manual override. The set switching status can also be locked by turning

the manual override (code R or as accessory).


Alternatives:

- A cover (code N or as accessory) can be fitted over the manual override to prevent it from being locked. The

manual override can then only be activated by pushing it.

- A cover (code V) can be fitted over the manual override to prevent it from being accidentally activated.

## Pneumatic connection and control elements




- 1 Flat plate silencer exhaust air 3/5
- 2 Manual override (for each pilot solenoid coil, non-detenting or detenting)
- 3 Adjusting knob for optional pressure regulator plate
- 4 Inscription label holder for sub-base
- 5 Working ports 2 and 4, for each valve position
- 6 Supply port 1
- 7 Pressure gauge (optional)
- 8 Ports 12 and 14 for supplying external pilot air

-  - Note

A manually actuated valve (manual override) cannot be reset electrically. Conversely, an electrically actuated valve cannot be reset using the mechanical manual override.

## Electrical connection and display components AS-interface



- 1 M12 socket AS-interface bus and additional supply (AS-i Out)
- 2 M12 plug AS-interface bus and additional supply (AS-i In)
- 3 Earth terminal
- 4 Status LEDs inputs
- 5 Status LEDs AS-interface
- 6 Diagnostic LEDs valves

General technical data				
Type	VMPA-...-4E4A-Z		VMPA-...-8E8A-Z	VMPA-...-8E8A-CE
Part No.	Order via order code/valve terminal configurator			
Valves	Number of solenoid coils	4		8
	Valve width [mm]	10, 14, 20		
	External power supply 24 V DC	Set using DIL switch		Yes
Inputs	No. of digital inputs	4		8
	Connection technology	5-pin M12, 3-pin M8, Harax, CageClamp, Sub-D		
	Sensor supply via AS-interface	Short circuit and overload proof		
	Sensor connection	2-wire and 3-wire sensors		
	Type	IEC 1131-2, type 02		
	Input circuitry	PNP (positive switching)		
AS-interface connection	Connection technology	M12 connection <sup>2)</sup>		
	Voltage range [V DC]	26.5 ... 31.6, reverse polarity protected		
	Residual ripple [mVss]	20		
	Current consumption of inputs	Without auxiliary power supply	With auxiliary power supply	With auxiliary power supply
	Basic electronic load	≤25	≤25	≤25
	Total input current	350	350	350
	Total output current (valves incl. LED) [mA]	MPA1: 270 MPA14: – MPA2: 533	MPA1: 540 MPA14: – MPA2: 1065	MPA1: 540 MPA14: – MPA2: 1065
Load voltage connection	Connection technology	M12 connection <sup>2)</sup>		
	Voltage range [V DC]	21.6 ... 26.4		
	Residual ripple [Vss]	4		
Current consumption of valves per solenoid coil	• Max. starting current (at 24 V) [mA]	MPA1: ≤80 MPA14: – MPA2: ≤100		
	• Following current reduction (approx. 25 ms) [mA]	MPA1: ≤25 MPA14: – MPA2: ≤20		
LED displays	ASI-LED	Green		
	AUX-PWR-LED	Green		
	FAULT-LED	Red		
	Inputs	Green		
	Valves	Yellow		
General data	Materials	Die-cast aluminium, PA		
	Note on materials	RoHS-compliant		
	Dimensions	➔ 48 ➔ Info 227		
	Weight [g]	360		
AS-interface data	ID code	ID = F <sub>H</sub> ; ID1 = F <sub>H</sub> <sup>1)</sup> ; ID2 = E <sub>H</sub>	ID = F <sub>H</sub> ; ID1 = F <sub>H</sub> <sup>1)</sup> ; ID2 = E <sub>H</sub>	ID = A <sub>H</sub> ; ID1 = F <sub>H</sub> <sup>1)</sup> ; ID2 = E <sub>H</sub>
	IO code	7 <sub>H</sub>	7 <sub>H</sub>	7 <sub>H</sub>
	Profile	S-7.F.E	S-7.F.E	S-7.A.E
	Addressing range	1 ... 31	1 ... 31	1A ... 31A, 1B ... 31B

1) Factory setting, set to 0<sub>H</sub> by some programming devices (Spec. V2.1) when addressing the slave

2) Suitable cable distributor from flat cable to M12 ➔ 49



Operating and environmental conditions	
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note about operating/pilot medium	Lubricated operation possible (subsequently required for further operation)
Operating pressure [bar]	–0.9 ... +10
Ambient temperature [°C]	–5 ... +50
Medium temperature [°C]	–5 ... +50
Storage temperature [°C]	–20 ... +40
Corrosion resistance class CRC <sup>1)</sup>	0
Relative air humidity	Max. 90% at 40 °C
CE mark (see declaration of conformity)	To EU EMC Directive <sup>2)</sup>
	To EU Explosion Protection Directive (ATEX)
KC mark	KC-EMC
Certification	c UL us - Recognized (OL)
	RCM trademark
Degree of protection	IP67

1) Corrosion resistance class CRC 0 to Festo standard FN 940070

No corrosion stress. Applies to small, optically irrelevant standard parts such as threaded pins, circlips and clamping sleeves which are usually only available in a phosphated or burnished version (and possibly oiled) as well as to ball bearings (for components < CRC 3) and plain bearings.

2) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: [www.festo.com/sp](http://www.festo.com/sp) → User documentation.

If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.















ATEX	
Type	MPA-ASI-VI
ATEX category gas	II 3 G
Ex-ignition protection type gas	Ex nA IIC T4 X Gc
Explosion-proof temperature rating [°C]	–5 ≤ Ta ≤ +50
CE mark (see declaration of conformity)	To EU Explosion Protection Directive (ATEX)







# AS-interface® components

MPA-S valve terminal – Connection blocks

FESTO


Combinations of connection blocks and electronics modules for inputs			
Connection blocks	Part No.	VMPA-...-8E8A	VMPA-...-4E4A
CPX-AB-4-M12X2-5POL	195704	■	■
CPX-AB-8-M8-3POL	195706	■	■
CPX-AB-8-KL-4POL	195708	■	■
CPX-AB-1-SUB-BU-25POL	525676	■	■
CPX-AB-4-HAR-4POL	525636	■	■

Pin allocation						
Connection block inputs		VMPA-...-8E8A		VMPA-...-4E4A		
CPX-AB-4-M12X2-5P-M3						
	 <b>X1</b>	 <b>X3</b>	X1.1: 24 V <sub>SEN</sub> X1.2: Input x+1 X1.3: 0 V <sub>SEN</sub> X1.4: Input x X1.5: FE (earth)	X3.1: 24 V <sub>SEN</sub> X3.2: Input x+5 X3.3: 0 V <sub>SEN</sub> X3.4: Input x+4 X3.5: FE (earth)	X1.1: 24 V <sub>SEN</sub> X1.2: Input x+1 X1.3: 0 V <sub>SEN</sub> X1.4: Input x X1.5: FE (earth)	
	 <b>X2</b>	 <b>X4</b>	X2.1: 24 V <sub>SEN</sub> X2.2: Input x+3 X2.3: 0 V <sub>SEN</sub> X2.4: Input x+2 X2.5: FE (earth)	X4.1: 24 V <sub>SEN</sub> X4.2: Input x+7 X4.3: 0 V <sub>SEN</sub> X4.4: Input x+6 X4.5: FE (earth)	X2.1: 24 V <sub>SEN</sub> X2.2: n.c. X2.3: 0 V <sub>SEN</sub> X2.4: Input x+1 X2.5: FE (earth)	X3.1: 24 V <sub>SEN</sub> X3.2: Input x+3 X3.3: 0 V <sub>SEN</sub> X3.4: Input x+2 X3.5: FE (earth)
CPX-AB-8-M8-3P-M3						
	 <b>X1</b>	 <b>X5</b>	X1.1: 24 V <sub>SEN</sub> X1.3: 0 V <sub>SEN</sub> X1.4: Input x	X5.1: 24 V <sub>SEN</sub> X5.3: 0 V <sub>SEN</sub> X5.4: Input x+4	X1.1: 24 V <sub>SEN</sub> X1.3: 0 V <sub>SEN</sub> X1.4: Input x	
	 <b>X2</b>	 <b>X6</b>	X2.1: 24 V <sub>SEN</sub> X2.3: 0 V <sub>SEN</sub> X2.4: Input x+1	X6.1: 24 V <sub>SEN</sub> X6.3: 0 V <sub>SEN</sub> X6.4: Input x+5	X2.1: 24 V <sub>SEN</sub> X2.3: 0 V <sub>SEN</sub> X2.4: Input x+1	X5.1: 24 V <sub>SEN</sub> X5.3: 0 V <sub>SEN</sub> X5.4: Input x+2
	 <b>X3</b>	 <b>X7</b>	X3.1: 24 V <sub>SEN</sub> X3.3: 0 V <sub>SEN</sub> X3.4: Input x+2	X7.1: 24 V <sub>SEN</sub> X7.3: 0 V <sub>SEN</sub> X7.4: Input x+6	X3.1: 24 V <sub>SEN</sub> X3.3: 0 V <sub>SEN</sub> X3.4: Input x+1	X6.1: 24 V <sub>SEN</sub> X6.3: 0 V <sub>SEN</sub> X6.4: Input x+3
	 <b>X4</b>	 <b>X8</b>	X4.1: 24 V <sub>SEN</sub> X4.3: 0 V <sub>SEN</sub> X4.4: Input x+3	X8.1: 24 V <sub>SEN</sub> X8.3: 0 V <sub>SEN</sub> X8.4: Input x+7	X4.1: 24 V <sub>SEN</sub> X4.3: 0 V <sub>SEN</sub> X4.4: n.c.	X7.1: 24 V <sub>SEN</sub> X7.3: 0 V <sub>SEN</sub> X7.4: Input x+3

Pin allocation					
Connection block inputs		VMPA-...-8E8A		VMPA-...-4E4A	
CPX-AB-8-KL-4P-M3					
		X1.0: 24 V <sub>SEN</sub> X1.1: 0 V <sub>SEN</sub> X1.2: Input x X1.3: FE (earth)	X5.0: 24 V <sub>SEN</sub> X5.1: 0 V <sub>SEN</sub> X5.2: Input x+4 X5.3: FE (earth)	X1.0: 24 V <sub>SEN</sub> X1.1: 0 V <sub>SEN</sub> X1.2: Input x X1.3: FE (earth)	X5.0: 24 V <sub>SEN</sub> X5.1: 0 V <sub>SEN</sub> X5.2: Input x+2 X5.3: FE (earth)
		X2.0: 24 V <sub>SEN</sub> X2.1: 0 V <sub>SEN</sub> X2.2: Input x+1 X2.3: FE (earth)	X6.0: 24 V <sub>SEN</sub> X6.1: 0 V <sub>SEN</sub> X6.2: Input x+5 X6.3: FE (earth)	X2.0: 24 V <sub>SEN</sub> X2.1: 0 V <sub>SEN</sub> X2.2: Input x+1 X2.3: FE (earth)	X6.0: 24 V <sub>SEN</sub> X6.1: 0 V <sub>SEN</sub> X6.2: Input x+3 X6.3: FE (earth)
		X3.0: 24 V <sub>SEN</sub> X3.1: 0 V <sub>SEN</sub> X3.2: Input x+2 X3.3: FE (earth)	X7.0: 24 V <sub>SEN</sub> X7.1: 0 V <sub>SEN</sub> X7.2: Input x+6 X7.3: FE (earth)	X3.0: 24 V <sub>SEN</sub> X3.1: 0 V <sub>SEN</sub> X3.2: Input x+1 X3.3: FE (earth)	X7.0: 24 V <sub>SEN</sub> X7.1: 0 V <sub>SEN</sub> X7.2: Input x+3 X7.3: FE (earth)
		X4.0: 24 V <sub>SEN</sub> X4.1: 0 V <sub>SEN</sub> X4.2: Input x+3 X4.3: FE (earth)	X8.0: 24 V <sub>SEN</sub> X8.1: 0 V <sub>SEN</sub> X8.2: Input x+7 X8.3: FE (earth)	X4.0: 24 V <sub>SEN</sub> X4.1: 0 V <sub>SEN</sub> X4.2: n.c. X4.3: FE (earth)	X8.0: 24 V <sub>SEN</sub> X8.1: 0 V <sub>SEN</sub> X8.2: n.c. X8.3: FE (earth)
CPX-AB-1-SUB-BU-25P-M3					
		1: Input x 2: Input x+1 3: Input x+2 4: Input x+3 5: 24 V <sub>SEN</sub> 6: 0 V <sub>SEN</sub> 7: 24 V <sub>SEN</sub> 8: 0 V <sub>SEN</sub> 9: 24 V <sub>SEN</sub> 10: 24 V <sub>SEN</sub> 11: 0 V <sub>SEN</sub> 12: 0 V <sub>SEN</sub> 13: FE (earth)	14: Input x+4 15: Input x+5 16: Input x+6 17: Input x+7 18: 24 V <sub>SEN</sub> 19: 24 V <sub>SEN</sub> 20: 24 V <sub>SEN</sub> 21: 24 V <sub>SEN</sub> 22: 0 V <sub>SEN</sub> 23: 0 V <sub>SEN</sub> 24: 0 V <sub>SEN</sub> 25: FE (earth) Socket: FE	1: Input x 2: Input x+1 3: Input x+1 4: n.c. 5: 24 V <sub>SEN</sub> 6: 0 V <sub>SEN</sub> 7: 24 V <sub>SEN</sub> 8: 0 V <sub>SEN</sub> 9: 24 V <sub>SEN</sub> 10: 24 V <sub>SEN</sub> 11: 0 V <sub>SEN</sub> 12: 0 V <sub>SEN</sub> 13: FE (earth)	14: Input x+2 15: Input x+3 16: Input x+3 17: n.c. 18: 24 V <sub>SEN</sub> 19: 24 V <sub>SEN</sub> 20: 24 V <sub>SEN</sub> 21: 24 V <sub>SEN</sub> 22: 0 V <sub>SEN</sub> 23: 0 V <sub>SEN</sub> 24: 0 V <sub>SEN</sub> 25: FE (earth) Socket: FE
CPX-AB-4-HAR-4P-M3					
		X1.1: 24 V <sub>SEN</sub> X1.2: Input x+1 X1.3: 0 V <sub>SEN</sub> X1.4: Input x	X3.1: 24 V <sub>SEN</sub> X3.2: Input x+5 X3.3: 0 V <sub>SEN</sub> X3.4: Input x+4	X1.1: 24 V <sub>SEN</sub> X1.2: Input x+1 X1.3: 0 V <sub>SEN</sub> X1.4: Input x	X3.1: 24 V <sub>SEN</sub> X3.2: Input x+3 X3.3: 0 V <sub>SEN</sub> X3.4: Input x+2
		X2.1: 24 V <sub>SEN</sub> X2.2: Input x+3 X2.3: 0 V <sub>SEN</sub> X2.4: Input x+2	X4.1: 24 V <sub>SEN</sub> X4.2: Input x+7 X4.3: 0 V <sub>SEN</sub> X4.4: Input x+6	X2.1: 24 V <sub>SEN</sub> X2.2: n.c. X2.3: 0 V <sub>SEN</sub> X2.4: Input x+1	X4.1: 24 V <sub>SEN</sub> X4.2: n.c. X4.3: 0 V <sub>SEN</sub> X4.4: Input x+3

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



- |                        |                        |                     |   |
|------------------------|------------------------|---------------------|---|
| 1 Solenoid valve MPA1  | 5 Supply/exhaust ports | 9 Mounting holes    | n Number of sub-bases in a grid of 4 MPA1, 4 MPA14 or 2 MPA2 valves |
| 2 Solenoid valve MPA2  | 6 Working ports        | 11 Connection block |   |
| 3 Solenoid valve MPA14 | 7 H-rail               | 12 Earthing screw   |   |
| 4 Manual override      | 8 H-rail mounting      | 18 Plug M12         |   |

Type	B1	B5	B6	B7	B8	B9	B10	B11	B12	B13	B14	B15	B18	B20	B21
MPA-S (ASI)	107.3	128.9	66.3	33.5	65	23.5	7.5	6.6	4.4	11	6.6	18	56	110.9	37.2

Type	D1	D2	H1	H3	H4	H7	H8	H9	H11	H13	H14	H16	H17	H21	H22
MPA-S (ASI)	M6	M4	108.1	59	56	23.9	23.1	10.8	45.1	22.1	20.3	8.7	8.2	55.1	53

Type	L1	L3 <sup>1)</sup>	L5 <sup>1)</sup>	L6	L7	L9	L10	L11	L12	L13	L14	L15
MPA-S (ASI)	85	n x 42	n x 65.5	17.9	20	6.5	5.6	6.5	9	14.5	1.5	13.5













Type	L16	L18	L19	L20	L22	L23	L24	L25	L26	L27	L28	L29
MPA-S (ASI)	1	21	10.5	5.2	16.7	18	18	7.7	12.6	14.8	14.8	9












1)  $n$  = number of sub-bases (with MPA1, width 10 mm and MPA14, width 14 mm, max. 4 valve positions on sub-base; with MPA2, width 20 mm, max. 2 valve positions on sub-base)

# AS-interface® components

MPA-S valve terminal – Accessories

**FESTO**













Ordering data				
	Description		Part No.	Type
Bus connection				
	AS-interface flat cable, yellow	100 m	18940	KASI-1,5-Y-100
	AS-interface flat cable, black	100 m	18941	KASI-1,5-Z-100
	Flat cable blanking plug		196090	ASI-SD-FK-BL
	AS-interface flat cable distributor	Parallel cable	18786	ASI-KVT-FK
	AS-interface flat cable distributor	Symmetrical cable	18797	ASI-KVT-FK-S
	Cable cap for flat cable (scope of delivery 50 pieces)		18787	ASI-KK-FK
	Cable sleeve (scope of delivery 20 pieces)		165593	ASI-KT-FK
	Socket M12, 4-pin	For AS-interface flat cable	18789	ASI-SD-PG-M12
	Socket M12, 5-pin	For round cable	18324	FBSD-GD-9-5POL
Cable distributor				
	AS-Interface data to socket M12, 4-pin		572225	NEFU-X22F-M12G4
	AS-Interface data and load voltage supply to socket M12, 4-pin		572226	NEFU-X24F-M12G4
	AS-Interface data and load voltage supply to socket M12, 4-pin, cable length 1 m		572227	NEFU-X24F-1-M12G4
DUO plug				
	Plug M12 for 2 sensor cables	4-pin, PG11	18779	SEA-GS-11-DUO
		5-pin, PG11	192010	SEA-5GS-11-DUO

Ordering data				
	Description		Part No.	Type
Sensor plugs				
	Straight sensor plug	M12, 4-pin, PG7	18666	SEA-GS-7
	Straight sensor plug	M12, 5-pin, PG7	175487	SEA-M12-5GS-PG7
	Straight sensor plug	M12, PG9 connector	18778	SEA-GS-9
	Straight sensor plug for cable Ø 2.5 mm	M12, 4-pin	192008	SEA-4GS-7-2,5
	Straight sensor plug	M8, screw-in, 3-pin	192009	SEA-3GS-M8-S
	Straight sensor plug	M8, solderable, 3-pin	18696	SEA-GS-M8
	Harax sensor plug	4-pin	525928	SEA-GS-HAR-4POL
	Sub-D plug	25-pin	527522	SD-SUB-D-ST25
	Cover cap (scope of delivery 10 pieces)	M12	165592	ISK-M12
		M8	177672	ISK-M8
Connecting cables				
	Modular system for connecting cables ➔ Internet: nebu		–	NEBU-...
	Straight plug M8, 3-pin, straight socket M8, 3-pin	0.5 m	541346	NEBU-M8G3-K-0.5-M8G3
		1.0 m	541347	NEBU-M8G3-K-1-M8G3
		2.5 m	541348	NEBU-M8G3-K-2.5-M8G3
		5.0 m	541349	NEBU-M8G3-K-5-M8G3
	Straight plug M12, 4-pin, straight socket M12, 5-pin	0.5 m	8000208	NEBU-M12G5-K-0.5-M12G4
T-type plug connector				
	Plug M12, A-coded, 4-pin	2x socket M12, A-coded, 5-pin	8005310	NEDY-L2R1-V1-M12G5-N-M12G4
		2x socket M8, A-coded, 3-pin	8005311	NEDY-L2R1-V1-M8G3-N-M12G4
	Modular system for sensor/actuator distributor ➔ Internet: nedy		–	NEDY-...

# AS-interface® components

MPA-S valve terminal – Accessories

**FESTO**

Ordering data				
	Description		Part No.	Type
Miscellaneous				
	Primary switched mode, modular power supply 24 V DC power supply	5 A	2247681	CACN-3A-1-5
		10 A	2247682	CACN-3A-1-10
	Addressing device (power supply plug included in scope of delivery)		18959	ASI-PRG-ADR
	Addressing cable		18960	KASI-ADR
	AS-interface input module for 8 inputs M8, compact		542124	ASI-8DI-M8-3POL
	AS-interface input/output module for 4 inputs/3 outputs M12, compact		542125	ASI-4DI3DO-M12X2-5POL-Z
	For foil Inscription label holder for sub-base, transparent, for paper foil label	can be used for VMPA1 VMPA2	533362	VMPA1-ST-1-4
		can be used for VMPA14	8085996	VMPA14-ST-1-4
	For IBS Inscription label holder for sub-base, 4-fold, for IBS-6x10	can be used for VMPA1 VMPA2	544384	VMPA1-ST-2-4
		can be used for VMPA14	8085997	VMPA14-ST-2-4
	Inscription labels 6x10mm in frames (64pieces)		18576	IBS 6x10
	H-rail to EN 60715		35430	NRH-35-2000
	H-rail mounting		526032	CPX-CPA-BG-NRH
	Mounting bracket		534416	VMPA-BG-RW
User's manual				
	MPA-S Pneumatics Description	German	534240	P.BE-MPA-DE
		English	534241	P.BE-MPA-EN
		French	534243	P.BE-MPA-FR
		Italian	534244	P.BE-MPA-IT
		Spanish	534242	P.BE-MPA-ES



## VTSA/VTSA-F valve terminals with AS-interface – Valve configuration options

VTSA/VTSA-F valve terminals with AS-interface can be flexibly configured with a wide range of valves. The system supports a maximum of 8 outputs (solenoid coils) and 8 inputs per valve terminal. This gives the following basic valve configuration options (see tables on following page).

### General data

- Solutions with integrated inputs
- Width 18, 26 (VTSA and VTSA-F) and 42, 52 mm (VTSA only)
- With or without 24 V DC auxiliary power supply for solenoid coils (EMERGENCY-STOP circuitry) in the case of the 4I/4O version. The auxiliary power supply is always integrated in the version with 8 inputs and cannot be subsequently switched off using the DIL switch
- Selectable bus connection technology
  - Flat cable for AS-interface with 4I/4O version
  - 4-pin M12 round plug<sup>1)</sup> with 4I/4O and 8I/8O version
- Selectable addressing
  - Via bus connection (M12 or flat cable)

### Versions

- 1 to 8 valves, freely configurable
- With 4 or 8 inputs
- M12, M8, quick connection, tension spring or Sub-D connection technology
- Separating seals for the creation of pressure zones
- Suitable for vacuum
- Subsequent extensions either
  - via vacant positions
  - by converting the valve terminal

### Application

- Flexible and cost-effective connection of 1 or 8 valves (max. 8 solenoid coils) with input feedback
- Decentralised machine and system structures, for example
  - in handling technology
  - in conveyor technology
  - in the packaging industry
  - in sorting systems
  - suitable for energy chains thanks to connection via round cables

### Note

Please follow the link below for more details on the various pneumatic functions.

- ➔ Internet: vtasa
- ➔ Internet: vtasa-f

<sup>1)</sup> Suitable cable distributor from flat cable to M12 ➔ 62

➔ Info 214 Valve terminal CPA



# AS-interface® components

VTSA/VTSA-F valve terminal – Connection technology and addressing

FESTO

Types of valve terminal with AS-interface									
Type	Valves	Solenoid coils	Inputs	Auxiliary power supply can be disconnected		Width (mm)			
				Yes	No	18	26	42 <sup>1)</sup>	52 <sup>1)</sup>
VTSA/VTSA-F-ASI-4E4A-Z	4	4	4	■	–	■	■	■	■
VTSA/VTSA-F-ASI-8E8A-Z	8	8	8	–	■	■	■	■	■

1) Width 42 and 52 mm not in the case of VTSA-F

Permissible combinations in valve position allocation (examples)				
Type	Slave n			
	0	1	2	3
4I/40 VTSA/VTSA-F – 18 and 26 mm (2 valves per sub-base)	M	M	M	M
	M	M	M	L
	M	M	–	–
	M	L	–	–
	...	...	...	...
	J	M	–	–
	M	J	–	–
	J	J	–	–
Special case	M	M	J	L
4I/40 VTSA – 42 mm (1 valve per sub-base)	M	M	M	M
	M	M	M	L
	M	M	–	–
	M	–	–	–
	...	...	...	...
	J	M	–	–
	J	M	M	–
	...	...	...	...
	M	J	M	–
	J	J	–	–

Permissible combinations in valve position allocation (examples)								
Type	Slave n plus slave n+1							
	0	1	2	3	4	5	6	7
8E8A VTSA/VTSA-F	M	M	M	M	M	M	M	M
	M	M	M	L	M	M	M	L
	...	...	...	...	...	...	...	...
	J	J	J	J	–	–	–	–
	J	J	J	M	–	–	–	–
	J	J	M	M	–	–	–	–
	...	...	...	...	...	...	...	...
	J	J	M	M	M	M	–	–
	...	...	...	...	...	...	...	...

1) All valve slices can be freely configured (up to the maximum number of valve solenoids supported (4 or 8).

A blanking plate can be used instead of the valve slice as a vacant position for one or two solenoid coils.

M Valve slice with single solenoid valve or a different valve slice with an output.

J Valve slice with double solenoid valve or a different valve slice with two outputs.

L Vacant position


# AS-interface® components

VTSA/VTSA-F valve terminal – Connection technology and addressing


FESTO

## Installation: Selectable connection technology for AS-interface


### Support for flat cables



- Straightforward cabling with flat cables in protected areas
- Fast system of installation with standard AS-interface cables
- Standard installation at the AS-interface with yellow flat cables is possible with the 4I/40 VTSA/VTSA-F version




### Support for round cables



Local round cable wiring system for areas subjected to consistently high stress:


- Permanently high humidity
- Need for flexible cabling using one cable
- Use in energy chains with highly flexible cables



- 1 Pre-assembled M12 round cable, 1 m, polyurethane
- 2 Selectable cable for additional slave, for example highly flexible cable for energy chains or PVC cable for applications requiring resistance to detergents


## Addressing

### Addressing device



- The addressing device to SPEC V2.1 can be used to scan the AS-interface from any point in the network. At all connected stations
- slave addresses can be read/changed
  - ID and IO codes can be read out
  - parameters can be read/changed
  - input/output data can be read and written (setting outputs)
  - error messages can be read out and quickly recognised

### AS-interface connections




- 1 M12 plug for AS-interface and incoming auxiliary supply
- 2 M12 socket for AS-interface and outgoing auxiliary supply

# AS-interface® components

VTSA/VTSA-F valve terminal – Connection technology and addressing

FESTO

## AS-interface flat cable distributor to round cable 2x M12



### Alternative connection concepts

- AS-interface connection technology for yellow and optionally for black flat cables
- Passive conversion of the signals to M12 socket and round cable via M12 socket
- Pre-assembled round cable, PUR, 1 m long
- Selectable PVC extension cable, 2.5 and 5 m, via additional M12 socket

### Selecting the cable

Optimised connection technologies at the AS-interface can be easily realised by selecting the right cable.


- Flat cables for all standard applications with installation-saving insulation displacement technology
- Round cables for applications with differing requirements, for example:
  - Energy chains with small radii and further requirements for highly flexible cables

- Applications with consistently high humidity
- Applications involving frequent cleaning and requiring cables resistant to detergents (PUR, PVC or other cables)
- Cabling systems using standard components (M12) preferred

### Easy to mount

- Direct mounting on a wall or machine frame

## Supplementary compact I/O modules



The valve terminals VTSA/VTSA-F can be supplemented with the compact I/O modules. The following are available:

- 8 inputs M8
- 4 inputs/3 outputs M12

# AS-interface® components

Key features – Display and operation

FESTO

## Display and operation

Each solenoid coil is allocated an LED which indicates its switching status.

- Indicator 12 shows the switching status of the pilot control for output 2
- Indicator 14 shows the switching status of the pilot control for output 4

### Manual override

The manual override enables the valve to be actuated when not electrically activated or energised.


The valve is activated by pushing the manual override. The set switching status can also be locked by turning the manual override.

### Alternatives:

- A cover (code N or as accessory) can be fitted over the manual override to prevent it from being locked. The valve can only be actuated by pressing it.

- A cover (code V) can be fitted over the manual override to prevent it from being accidentally activated.

## Pneumatic connection and control elements




- 1 Pressure gauge (optional)
- 2 Adjusting knob for optional pressure regulator plate
- 3 Manual override (for each pilot solenoid coil, non-detenting or detenting)
- 4 Optional cover for manual override (prevents manual override)
- 5 Optional cover for manual override with non-detenting/pushing function
- 6 Inscription label holder for valve
- 7 Adjusting screw of optional flow control plate
- 8 Exhaust ports (valves) (3/5)
- 9 Pilot ports 12 and 14 for supplying the external pilot air supply
- 10 Inscription label holder for sub-base
- 11 Supply port 1 (operating pressure)
- 12 Working ports 2 and 4, for each valve position



### Note

A manually actuated valve (manual override) cannot be reset electrically. Conversely, an electrically actuated valve cannot be reset using the mechanical manual override.

## Electrical connection and display components



- 1 M12 socket AS-interface bus and additional supply (AS-i Out)
- 2 M12 plug AS-interface bus and additional supply (AS-i In)
- 3 Earth terminal
- 4 Status LEDs inputs
- 5 Status LEDs AS-interface
- 6 Diagnostic LEDs valves

# AS-interface® components

VTSA/VTSA-F valve terminal

FESTO

Technical data					
Type		VTSA/VTSA-F-ASI-4E4A-Z		VTSA/VTSA-F-ASI-8E8A-Z	
Part No.		Order via order code/valve terminal configurator			
Assembly position		Any			
Digital inputs	No. of digital inputs	4		8	
	Connection technology	5-pin M12, 3-pin M8, quick connection, tension spring, Sub-D			
	Sensor supply via AS-interface	Short circuit and overload proof			
	Sensor connection	2-wire and 3-wire sensors			
	Type	IEC 1131-2, type 02			
	Input circuitry	PNP (positive switching)			
Valves	Number of solenoid coils	4		8	
	Valve width	[mm]	18/26/42/52 (width 42 and 52 mm only in the case of VTSA)		
	External power supply 24 V DC (auxiliary power supply)	Set using DIL switch		Yes	
Max. current consumption of valves per solenoid coil		[mA]	90		
AS-interface connection	Connection technology	Plug M12x1, 4-pin; socket M12x1, 4-pin <sup>2)</sup>			
	Voltage range	[V DC]	26.5 ... 31.6, reverse polarity protected		
	Residual ripple	[mVss]	20		
	Electrical isolation fieldbus interface	Optocoupler			
	Current consumption of inputs	[mA]	Without auxiliary power supply	With auxiliary power supply	With auxiliary power supply
	Basic electronic load		≤25	≤25	≤25
	Total input current		350	350	350
	Total current consumption		Max. 500	Max. 700	Max. 700
Load voltage connection	Connection technology	M12 connection <sup>2)</sup>			
	Voltage range	[V DC]	21.6 ... 26.4		
	Residual ripple	[Vss]	4		
LED displays	ASI-LED	Green			
	AUX-PWR-LED	Green			
	FAULT-LED	Red			
	Inputs	Green			
	Valves	Yellow			
AS-interface data	AS-interface specification	AS-interface Complete Spec 3.0			
	Addressing range Slave	0, 1 ... 31			
	ID code	ID = F <sub>H</sub> ; ID1 = F <sub>H</sub> <sup>1)</sup> ; ID2 = E <sub>H</sub>			
	IO code	7 <sub>H</sub>			
	Profile	S-7.F.E			

1) Factory setting, set to 0<sub>H</sub> by some programming devices (Spec. V2.1) when addressing the slave

2) Suitable cable distributor from flat cable to M12 → 62

Operating and environmental conditions		
Protection class (to EN 60529)		IP65, NEMA 4 (in assembled state)
Electromagnetic compatibility		Tested to 50295
CE mark (see declaration of conformity)		To EU EMC Directive
		To EU Low Voltage Directive
Certification		c UL us - Recognized (OL)
		C-Tick
Ambient temperature	[°C]	−5 ... +50
Storage temperature	[°C]	−20 ... +40
Materials	Housing	Die-cast aluminium, PA
	Seals	NBR, PUR
Note on materials		RoHS-compliant
Weight	[g]	AS-interface connection: 300, multi-pin node: 850

# AS-interface® components

VTSA/VTSA-Fvalve terminal – Connection blocks

FESTO



Note

The valve terminal VTSA with AS-interface connection is based on the same electrical manifold module as the valve terminal with multi-pin plug connection. This means it is possible to convert a valve terminal with

multi-pin plug connection using an AS-interface module. The technical specifications of the AS-interface system must be observed in this case.







➔ Internet: vtsa

## Combinations of connection blocks and electronics modules for inputs

Connection blocks	Part No.	VTSA/VTSA-F-ASI-8E8A-Z	VTSA/VTSA-F-ASI-4E4A-Z
CPX-AB-4-M12x2-5POL	195704	■	■
CPX-AB-4-M12x2-5POL-R	541254	■	■
CPX-AB-8-KL-4POL	195708	■	■
CPX-AB-1-Sub-BU-25POL	525676	■	■
CPX-AB-4-HAR-4POL	525636	■	■
CPX-AB-8-M8-3POL	195706	■	■

## Pin allocation

Connection block inputs	VTSA/VTSA-F-ASI-8E8A-Z		VTSA/VTSA-F-ASI-4E4A-Z	
CPX-AB-4-M12X2-5POL				
	X1.1: 24 V <sub>SEN</sub> X1.2: Input x+1 X1.3: 0 V <sub>SEN</sub> X1.4: Input x X1.5: FE (earth)  X2.1: 24 V <sub>SEN</sub> X2.2: Input x+3 X2.3: 0 V <sub>SEN</sub> X2.4: Input x+2 X2.5: FE (earth)	X3.1: 24 V <sub>SEN</sub> X3.2: Input x+5 X3.3: 0 V <sub>SEN</sub> X3.4: Input x+4 X3.5: FE (earth)  X4.1: 24 V <sub>SEN</sub> X4.2: Input x+7 X4.3: 0 V <sub>SEN</sub> X4.4: Input x+6 X4.5: FE (earth)	X1.1: 24 V <sub>SEN</sub> X1.2: Input x+1 X1.3: 0 V <sub>SEN</sub> X1.4: Input x X1.5: FE (earth)  X2.1: 24 V <sub>SEN</sub> X2.2: n.c. X2.3: 0 V <sub>SEN</sub> X2.4: Input x+1 X2.5: FE (earth)	X3.1: 24 V <sub>SEN</sub> X3.2: Input x+3 X3.3: 0 V <sub>SEN</sub> X3.4: Input x+2 X3.5: FE (earth)  X4.1: 24 V <sub>SEN</sub> X4.2: n.c. X4.3: 0 V <sub>SEN</sub> X4.4: Input x+3 X4.5: FE (earth)
CPX-AB-8-M8-3POL				
	X1.1: 24 V <sub>SEN</sub> X1.3: 0 V <sub>SEN</sub> X1.4: Input x  X2.1: 24 V <sub>SEN</sub> X2.3: 0 V <sub>SEN</sub> X2.4: Input x+1  X3.1: 24 V <sub>SEN</sub> X3.3: 0 V <sub>SEN</sub> X3.4: Input x+2  X4.1: 24 V <sub>SEN</sub> X4.3: 0 V <sub>SEN</sub> X4.4: Input x+3	X5.1: 24 V <sub>SEN</sub> X5.3: 0 V <sub>SEN</sub> X5.4: Input x+4  X6.1: 24 V <sub>SEN</sub> X6.3: 0 V <sub>SEN</sub> X6.4: Input x+5  X7.1: 24 V <sub>SEN</sub> X7.3: 0 V <sub>SEN</sub> X7.4: Input x+6  X8.1: 24 V <sub>SEN</sub> X8.3: 0 V <sub>SEN</sub> X8.4: Input x+7	X1.1: 24 V <sub>SEN</sub> X1.3: 0 V <sub>SEN</sub> X1.4: Input x  X2.1: 24 V <sub>SEN</sub> X2.3: 0 V <sub>SEN</sub> X2.4: Input x+1  X3.1: 24 V <sub>SEN</sub> X3.3: 0 V <sub>SEN</sub> X3.4: Input x+1  X4.1: 24 V <sub>SEN</sub> X4.3: 0 V <sub>SEN</sub> X4.4: n.c.	X5.1: 24 V <sub>SEN</sub> X5.3: 0 V <sub>SEN</sub> X5.4: Input x+2  X6.1: 24 V <sub>SEN</sub> X6.3: 0 V <sub>SEN</sub> X6.4: Input x+3  X7.1: 24 V <sub>SEN</sub> X7.3: 0 V <sub>SEN</sub> X7.4: Input x+3  X8.1: 24 V <sub>SEN</sub> X8.3: 0 V <sub>SEN</sub> X8.4: n.c.

Pin allocation		VTSA/VTSA-F-ASI-8E8A-Z		VTSA/VTSA-F-ASI-4E4A-Z	
CPX-AB-8-KL-4POL					
		X1.0: 24 V <sub>SEN</sub> X1.1: 0 V <sub>SEN</sub> X1.2: Input x X1.3: FE (earth)	X5.0: 24 V <sub>SEN</sub> X5.1: 0 V <sub>SEN</sub> X5.2: Input x+4 X5.3: FE (earth)	X1.0: 24 V <sub>SEN</sub> X1.1: 0 V <sub>SEN</sub> X1.2: Input x X1.3: FE (earth)	X5.0: 24 V <sub>SEN</sub> X5.1: 0 V <sub>SEN</sub> X5.2: Input x+2 X5.3: FE (earth)
		X2.0: 24 V <sub>SEN</sub> X2.1: 0 V <sub>SEN</sub> X2.2: Input x+1 X2.3: FE (earth)	X6.0: 24 V <sub>SEN</sub> X6.1: 0 V <sub>SEN</sub> X6.2: Input x+5 X6.3: FE (earth)	X2.0: 24 V <sub>SEN</sub> X2.1: 0 V <sub>SEN</sub> X2.2: Input x+1 X2.3: FE (earth)	X6.0: 24 V <sub>SEN</sub> X6.1: 0 V <sub>SEN</sub> X6.2: Input x+3 X6.3: FE (earth)
		X3.0: 24 V <sub>SEN</sub> X3.1: 0 V <sub>SEN</sub> X3.2: Input x+2 X3.3: FE (earth)	X7.0: 24 V <sub>SEN</sub> X7.1: 0 V <sub>SEN</sub> X7.2: Input x+6 X7.3: FE (earth)	X3.0: 24 V <sub>SEN</sub> X3.1: 0 V <sub>SEN</sub> X3.2: Input x+1 X3.3: FE (earth)	X7.0: 24 V <sub>SEN</sub> X7.1: 0 V <sub>SEN</sub> X7.2: Input x+3 X7.3: FE (earth)
		X4.0: 24 V <sub>SEN</sub> X4.1: 0 V <sub>SEN</sub> X4.2: Input x+3 X4.3: FE (earth)	X8.0: 24 V <sub>SEN</sub> X8.1: 0 V <sub>SEN</sub> X8.2: Input x+7 X8.3: FE (earth)	X4.0: 24 V <sub>SEN</sub> X4.1: 0 V <sub>SEN</sub> X4.2: n.c. X4.3: FE (earth)	X8.0: 24 V <sub>SEN</sub> X8.1: 0 V <sub>SEN</sub> X8.2: n.c. X8.3: FE (earth)
CPX-AB-1-SUB-BU-25POL					
		1: Input x 2: Input x+1 3: Input x+2 4: Input x+3 5: 24 V <sub>SEN</sub> 6: 0 V <sub>SEN</sub> 7: 24 V <sub>SEN</sub> 8: 0 V <sub>SEN</sub> 9: 24 V <sub>SEN</sub> 10: 24 V <sub>SEN</sub> 11: 0 V <sub>SEN</sub> 12: 0 V <sub>SEN</sub> 13: FE (earth)	14: Input x+4 15: Input x+5 16: Input x+6 17: Input x+7 18: 24 V <sub>SEN</sub> 19: 24 V <sub>SEN</sub> 20: 24 V <sub>SEN</sub> 21: 24 V <sub>SEN</sub> 22: 0 V <sub>SEN</sub> 23: 0 V <sub>SEN</sub> 24: 0 V <sub>SEN</sub> 25: FE (earth) Socket: FE	1: Input x 2: Input x+1 3: Input x+1 4: n.c. 5: 24 V <sub>SEN</sub> 6: 0 V <sub>SEN</sub> 7: 24 V <sub>SEN</sub> 8: 0 V <sub>SEN</sub> 9: 24 V <sub>SEN</sub> 10: 24 V <sub>SEN</sub> 11: 0 V <sub>SEN</sub> 12: 0 V <sub>SEN</sub> 13: FE (earth)	14: Input x+2 15: Input x+3 16: Input x+3 17: n.c. 18: 24 V <sub>SEN</sub> 19: 24 V <sub>SEN</sub> 20: 24 V <sub>SEN</sub> 21: 24 V <sub>SEN</sub> 22: 0 V <sub>SEN</sub> 23: 0 V <sub>SEN</sub> 24: 0 V <sub>SEN</sub> 25: FE (earth) Socket: FE
CPX-AB-4-HAR-4POL					
		X1.1: 24 V <sub>SEN</sub> X1.2: Input x+1 X1.3: 0 V <sub>SEN</sub> X1.4: Input x	X3.1: 24 V <sub>SEN</sub> X3.2: Input x+5 X3.3: 0 V <sub>SEN</sub> X3.4: Input x+4	X1.1: 24 V <sub>SEN</sub> X1.2: Input x+1 X1.3: 0 V <sub>SEN</sub> X1.4: Input x	X3.1: 24 V <sub>SEN</sub> X3.2: Input x+3 X3.3: 0 V <sub>SEN</sub> X3.4: Input x+2
		X2.1: 24 V <sub>SEN</sub> X2.2: Input x+3 X2.3: 0 V <sub>SEN</sub> X2.4: Input x+2	X4.1: 24 V <sub>SEN</sub> X4.2: Input x+7 X4.3: 0 V <sub>SEN</sub> X4.4: Input x+6	X2.1: 24 V <sub>SEN</sub> X2.2: n.c. X2.3: 0 V <sub>SEN</sub> X2.4: Input x+1	X4.1: 24 V <sub>SEN</sub> X4.2: n.c. X4.3: 0 V <sub>SEN</sub> X4.4: Input x+3


# AS-interface® components

VTSA/VTSA-F valve terminal – Dimensions

FESTO

## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



- 1 Solenoid valve 18 mm
- 2 Solenoid valve 26 mm
- 3 Solenoid valve 42 mm  
(not in the case of VTSA-F)
- 4 Solenoid valve 52 mm  
(not in the case of VTSA-F)
- 5 Threaded connection G1/2 or  
1/2NPT
- 6 Threaded connection G3/8 or  
3/8NPT

- 7 Threaded connection G1/4 or  
1/4NPT
- 8 Threaded connection G1/8 or  
1/8NPT
- 9 H-rail
- 10 H-rail mounting
- 11 Mounting hole

- 12 Additional mounting bracket
- 13 Inscription label
- 14 End plate
- 15 Plug M12
- 16 Additional mounting bracket
- 17 Cover cap/manual override


- n02 Number of manifold blocks  
38 mm
- n01 Number of manifold blocks  
54 mm
- n1 Number of manifold blocks  
43 mm
- n2 Number of manifold blocks  
59 mm
- nzwp Number of supply plates

Width	L1
18 mm	$71.3 + n02 \times 38 + nzwp \times 38 + 37.3$
26 mm	$71.3 + n01 \times 54 + nzwp \times 38 + 37.3$
42 mm	$71.3 + n1 \times 43 + nzwp \times 38 + 37.3$
52 mm	$71.3 + n2 \times 59 + nzwp \times 38 + 37.3$
Mixture of 18 mm, 26 mm, 42 mm and 52 mm	$71.3 + n02 \times 38 + n01 \times 54 + n1 \times 43 + n2 \times 59 + nzwp \times 38 + 37.3$



VTSA/VTSA-F valve terminal with soft-start valve

**FESTO**

Download CAD data → [www.festo.com](http://www.festo.com)













- |          |   |           |                                    |           |                             |     |                           |
|----------|---|-----------|------------------------------------|-----------|-----------------------------|-----|---------------------------|
| <b>1</b> | Solenoid valve 18 mm                                | <b>7</b>  | Threaded connection G1/4 or 1/4NPT | <b>14</b> | End plate                   | n02 | Number of manifold blocks |
| <b>2</b> | Solenoid valve 26 mm                                |           |                                    | <b>15</b> | Plug M12                    |     | 38 mm                     |
| <b>3</b> | Solenoid valve 42 mm<br>(not in the case of VTSA-F) | <b>8</b>  | Threaded connection G1/8 or 1/8NPT | <b>16</b> | Additional mounting bracket | n01 | Number of manifold blocks |
| <b>4</b> | Solenoid valve 52 mm<br>(not in the case of VTSA-F) | <b>9</b>  | H-rail                             | <b>17</b> | Proximity sensor M12x1      |     | 54 mm                     |
|          |   | <b>10</b> | H-rail mounting                    | <b>18</b> | Cover cap/manual override   | n1  | Number of manifold blocks |
| <b>5</b> | Threaded connection G1/2 or 1/2NPT                  | <b>11</b> | Mounting hole                      | <b>19</b> | Soft-start valve 43 mm      |     | 43 mm                     |
| <b>6</b> | Threaded connection G3/8 or 3/8NPT                  | <b>12</b> | Additional mounting bracket        |           |                             | n2  | Number of manifold blocks |
|          |   | <b>13</b> | Inscription label                  |           |                             |     | 59 mm                     |
|          |   |           |                                    |           |                             | nzw | Number of supply plates   |

Width	L1
18 mm	$71.3 + n02 \times 38 + nzwp \times 38 + 37.3$
26 mm	$71.3 + n01 \times 54 + nzwp \times 38 + 37.3$
42 mm	$71.3 + n1 \times 43 + nzwp \times 38 + 37.3$
52 mm	$71.3 + n2 \times 59 + nzwp \times 38 + 37.3$
Mixture of 18 mm, 26 mm, 42 mm and 52 mm	$71.3 + n02 \times 38 + n01 \times 54 + n1 \times 43 + n2 \times 59 + nzwp \times 38 + 37.3$

# AS-interface® components

VTSA/VTSA-Fvalve terminal – Accessories












**FESTO**

Ordering data				
	Description		Part No.	Type
Bus connection				
	AS-interface flat cable, yellow	100 m	18940	KASI-1,5-Y-100
	AS-interface flat cable, black	100 m	18941	KASI-1,5-Z-100
	Flat cable blanking plug		196090	ASI-SD-FK-BL
	AS-interface flat cable distributor	Parallel cable	18786	ASI-KVT-FK
	AS-interface flat cable distributor	Symmetrical cable	18797	ASI-KVT-FK-S
	Cable cap for flat cable (scope of delivery 50 pieces)		18787	ASI-KK-FK
	Cable sleeve (scope of delivery 20 pieces)		165593	ASI-KT-FK
	Socket M12, 4-pin	For AS-interface flat cable	18789	ASI-SD-PG-M12
	Socket M12, 5-pin	For round cable	18324	FBSD-GD-9-5POL
Cable distributor				
	AS-Interface data to socket M12, 4-pin		572225	NEFU-X22F-M12G4
	AS-Interface data and load voltage supply to socket M12, 4-pin		572226	NEFU-X24F-M12G4
	AS-Interface data and load voltage supply to socket M12, 4-pin, cable length 1 m		572227	NEFU-X24F-1-M12G4
DUO plug				
	Plug M12 for 2 sensor cables	4-pin, PG11	18779	SEA-GS-11-DUO
		5-pin, PG11	192010	SEA-5GS-11-DUO

# AS-interface® components

VTSA/VTSA-Fvalve terminal – Accessories











**FESTO**

Ordering data				
	Description		Part No.	Type
Sensor plugs				
	Straight sensor plug	M12, 4-pin, PG7	18666	SEA-GS-7
	Straight sensor plug	M12, 5-pin, PG7	175487	SEA-M12-5GS-PG7
	Straight sensor plug	M12, PG9 connector	18778	SEA-GS-9
	Straight sensor plug for cable Ø 2.5 mm	M12, 4-pin	192008	SEA-4GS-7-2,5
	Straight sensor plug	M8, screw-in, 3-pin	192009	SEA-3GS-M8-S
	Straight sensor plug	M8, solderable, 3-pin	18696	SEA-GS-M8
	Harax sensor plug	4-pin	525928	SEA-GS-HAR-4POL
	Sub-D plug	25-pin	527522	SD-SUB-D-ST25
	Cover cap (scope of delivery 10 pieces)	M12	165592	ISK-M12
		M8	177672	ISK-M8
Connecting cable				
	Modular system for connecting cables ➔ Internet: nebu		–	NEBU-...
	Straight plug M8, 3-pin, straight socket M8, 3-pin	0.5 m	541346	NEBU-M8G3-K-0.5-M8G3
		1.0 m	541347	NEBU-M8G3-K-1-M8G3
		2.5 m	541348	NEBU-M8G3-K-2.5-M8G3
		5.0 m	541349	NEBU-M8G3-K-5-M8G3
	Straight plug M12, 4-pin, straight socket M12, 5-pin	0.5 m	8000208	NEBU-M12G5-K-0.5-M12G4
T-type plug connector				
	Plug M12, A-coded, 4-pin	2x socket M12, A-coded, 5-pin	8005310	NEDY-L2R1-V1-M12G5-N-M12G4
		2x socket M8, A-coded, 3-pin	8005311	NEDY-L2R1-V1-M8G3-N-M12G4
	Modular system for sensor/actuator distributor ➔ Internet: nedy		–	NEDY-...

# AS-interface® components

VTSA/VTSA-F valve terminal – Accessories


**FESTO**

Ordering data				
	Description		Part No.	Type
Miscellaneous				
	Primary switched mode, modular power supply 24 V DC power supply	5 A	2247681	CACN-3A-1-5
		10 A	2247682	CACN-3A-1-10
	Addressing device (power supply plug included in scope of delivery)		18959	ASI-PRG-ADR
	Addressing cable		18960	KASI-ADR
	AS-interface input module for 8 inputs M8		542124	ASI-8DI-M8-3POL
	AS-interface input/output module for 4 inputs/3 outputs M12		542125	ASI-4DI3DO-M12X2-5POL-Z
	Clip-on inscription label holder for valve cap (pack of 5)		540888	ASCF-T-S6
	Inscription label holder for connection blocks (pack of 5)		540889	ASCF-M-S6
	H-rail to EN 60715		35430	NRH-35-2000
	H-rail mounting		526032	CPX-CPA-BG-NRH
User's manual				
	Description of the valve terminal VTSA/VTSA-F	German	538922	P.BE-VTSA-44-DE
		English	538923	P.BE-VTSA-44-EN
		French	538925	P.BE-VTSA-44-FR
		Italian	538926	P.BE-VTSA-44-IT
		Spanish	538924	P.BE-VTSA-44-ES

## AS-interface® components

Compact I/O modules and valve interfaces to Spec. V2.1

FESTO



### Compact I/O modules to Spec. V2.1

#### General description

- Highly compact modules
- Encapsulated, sturdy electronics
- Inputs/outputs to IEC1131, PNP
- Short circuit proof, overload proof
- Inputs suitable for proximity sensors, inductive, capacitive or optical sensors and light barriers
- Ideal for use in decentralised handling and assembly as well as universal applications with increased requirements
- AS-interface Specification V2.11
- A/B mode
- Bus and auxiliary power supply looped through via 2x M12
- Quick installation
- Individual module diagnostics

#### Module with 8 inputs

- Two slaves in one housing
- 8 inputs M8, 3-pin, 200 mA per input
- Peripherals faults per slave, two fault LEDs
- Status display per input
- Supply exclusively from "yellow" AS-interface cable, the pins for the auxiliary power supply are simply looped through
- This permits cascading of the input/output modules

#### Module with 4 inputs/3 outputs


- Individual slave
- 4 inputs M12, 5-pin, with double allocation, 200 mA per input
- 3 outputs M12, 5-pin, with double allocation, 1 A per output
- Peripherals fault, fault LED
- Status display for each input and output
- Inputs are supplied exclusively from the "yellow" AS-interface cable
- Outputs are supplied exclusively from the "black" AS-interface cable

# AS-interface® components

Compact I/O modules and valve interfaces

FESTO

## Applications



The M12 bus connection standardised in the AS-interface specification offers various advantages:

- Use of standardised, pre-assembled M12 connecting cables
- One cable instead of two
- Installation-saving, quick M12 screw-type lock
- Flexible selection and optimisation of the necessary cable qualities in areas with permanently high stress, for example for

- energy chains
- robot arms (torsion)
- environments with higher moisture content
- aggressive media


This connection technology makes compact modules ideal for use both in demanding and extremely tight conditions.

Decentralised machine and system structures, for example


- Handling technology
- Conveyor technology
- Packaging industry
- Sorting systems
- Upstream functions via energy chains and robot arms

## Tips on use


- In addition to valve terminals for optimising the number of inputs.




- Suitable for valve terminals with M12 bus connection for looping through the bus via M12



- Universal applications for all commonly used sensors and light barriers up to 200 mA per channel



- Universal outputs 1 A, up to 2 A (approx. 50 W) can be connected by means of parallel connection in the DUO plug




# AS-interface® components

Compact I/O modules and valve interfaces

FESTO

## AS-interface flat cable distributor to round cable 2x M12



### Alternative connection concepts

- AS-interface connection technology for yellow and optionally for black flat cables
- Passive conversion of the signals to M12 socket and round cable via M12 socket
- Pre-assembled round cable, PUR, 1 m long
- Alternatively PVC extension cable, or another suitable cable of any length, via additional M12 socket

### Selecting the cable

Optimised connection technologies at the AS-interface can be easily achieved by selecting the right cable.

- Flat cables for all standard applications with installation-saving insulation displacement technology
- Round cables for applications with differing requirements, for example:
  - Energy chains with small radii and further requirements for highly flexible cables

- Applications with consistently high humidity
- Applications involving frequent cleaning and requiring cables resistant to detergents (PUR, PVC or other cables)
- Cabling systems using standard components (M12) preferred

### Easy to fit

- Direct mounting on a wall or machine frame

## Tips on use and installation (inputs/outputs)


### Input module 8DI-M8

Connection technologies based on M8 take account of the increasing trend towards miniaturisation. Sensors with

pre-assembled M8 connecting cables or with M8 plugs can be directly connected in a 1:1 relationship. This

simplifies allocation and troubleshooting. Individual sensors or cables

can be easily and quickly replaced in the event of faults.



# AS-interface® components

Compact I/O modules and valve interfaces

FESTO

## Tips on use and installation (inputs/outputs)

### Input/output module 4DI3DO-M12


Sturdy M12 connection technology is still an accepted standard for inputs and outputs. Direct connection for sensors with M12 connection. The M12 interfaces with double allocation can be split into 2xM12 or 2xM8 via DUO plugs, DUO cables or T-adapters.

The standard for valves with central plug (EN 60947-5-2 and ISO 20401) defines double allocation for M12 or M8. This means that a double solenoid valve and a single solenoid valve can be directly connected to a

compact AS-interface module using a 1:1 connection. This simplifies allocation and troubleshooting. Individual valves or cables can be easily and quickly replaced in the event of faults.

-  - Note

M8 4-pin adapter cables can be configured to M12 5-pin in Festo's modular system for connecting cables (NEBU...) so that even compact valve plugs as in MPA-S can be directly connected via pre-assembled cables.





# AS-interface® components

Compact I/O modules and valve interfaces

FESTO

## Tips on use and installation (AS-interface)

The compact I/O modules feature 4-pin M12 connections for bus IN and bus OUT. As per the AS-interface

specification, the two signal cables for the bus and the optional 24 V DC auxiliary power supply are accommodated


on this one connection. All 4 connections are looped through so that a number of modules and even

subsequent valve terminals can be cascaded.

### Input module 8DI-M8


Supply to the inputs is provided exclusively from the "yellow" AS-interface cable at this module, i.e. the pins for the auxiliary power supply are not used. This means that the following connection technologies can be realised in addition to the connections via M12 round plug connectors:

- Cable distributor NEFU-X2, directly assembled.
- This permits cost-effective and quick connection of a number of directly adjacent modules.
- A transition to valve terminals such as CPV is possible directly and without converters.



If there is an input module at the end of a string, the flat cable can also be routed through a specially sealed connector.

- Connection socket ASI-SD-PG-M12, directly assembled.
- Use at valve terminals with M12 is also possible, provided the auxiliary power supply is not required.




### Input/output module 4DI3DO-M12

Supply to the inputs is provided exclusively from the "yellow" AS-interface cable and supply to the outputs is provided exclusively from the "black" AS-interface cable at this module. Supply is provided either completely by an M12 installation or by means of a suitable converter such as the flat cable distributor NEFU-X24F-M12G4.

- - - Note

The contact load capacity of an M12 pin is limited to 4 A. With cascaded modules, ensure that the maximum current load of the first M12 connection in a series will not be exceeded even in a worst case scenario.



## Voltage drop on cables with M12 connection


Note that the voltage drop on an M12 cable is higher than on the AS-interface flat cable due to the smaller cable cross sections. The cable

lengths must be sized in accordance with the permissible voltage tolerances for the AS-interface signal and

the outputs for consuming devices with additional load voltage. The following graphs provide an initial


orientation (non-linear scaling of the cable length):

Voltage drop U (V) for cable cross section 0.34 mm<sup>2</sup> with M12



- - - 0.5 A  
 — 1 A  
 - - - 2 A  
 - - - 3 A  
 - - - 4 A

Voltage drop U (V) for cable cross section 0.25 mm<sup>2</sup> with M12



- - - 0.5 A  
 — 1 A  
 - - - 2 A  
 - - - 3 A  
 - - - 4 A

# AS-interface® components

Compact I/O modules and valve interfaces

FESTO

## Installation



### Installation for consuming devices with high current consumption

If several amperes are to be tapped per module, a suitable supply must be ensured via the corresponding

number of distributors (see the following example). This means that the

max. 3 A per module can be simultaneously switched. Note also that the

voltage drop increases with large currents in the flat cables (2 x 1.5 mm<sup>2</sup>).




### Alternative M12 installation with branch lines

Installation via branch lines can also be selected for straight M12

installation as an alternative to the looped-through AS-i bus.

The T-adapter FB-TA-M12-5POL is ideal for this (bus IN: socket, bus OUT:

plug).



# AS-interface® components

Compact I/O modules and valve interfaces

FESTO

## Assembly of the compact AS-interface modules

### Wall mounting

The AS-interface modules can be mounted on flat surfaces in almost

any position using the existing mounting holes and two M4 screws.




Note

The modules are protected against short circuit using a thermal fuse. This can result in the housing heating up to over 100 °C with short circuits of long duration.


You should therefore install the modules on a base and in an environment designed for this temperature and which is free of fire risk due to ignition (ATEX category T4 – up to 135°).

### Wall mounting – Compact I/O modules




With the compact I/O modules, the mounting holes are covered by inscription labels.

### Mounting on profiles (ITEM, etc.)



With slot nuts for M4, otherwise see wall mounting.

### H-rail mounting



A mounting kit is available that can be used on an H-rail. On the compact CP modules, the mounting holes are covered by inscription labels.

The following mounting kit is required for H-rail mounting:

- CP-TS-HS35
- This enables mounting on H-rails to EN 60715.

# AS-interface® components

Compact I/O modules and valve interfaces

FESTO

## Function

Digital input modules facilitate the connection of proximity sensors or other digital 24 V DC sensors (inductive, capacitive, light barriers, etc.), PNP.

## Applications

- Input module for 24 V DC sensor signals
- Double slave, two slaves in one housing
- M8 plug connection technology, single allocation
- The input status of each input signal is indicated on an allocated green LED
- 24 V DC supply for all connected sensors provided via the ("yellow") AS-interface cable
- Peripherals fault LED for short circuit/undervoltage of sensor supply for each AS-interface slave
- Modules support A/B mode in accordance with Spec. V2.11
- Bus connection 2x M12 for bus in and bus out
- Bus and auxiliary power supply looped through for cascading with output modules



General technical data		
Type	ASI-8DI-M8-3POL	
Digital inputs	No. of inputs	8
	Power supply 24 V DC	From the AS-interface ("yellow" cable)
	Intrinsic current consumption of electronics [mA]	Typically 35 (inputs not connected)
	Input current at 24 V DC (from sensor) [mA]	Typically 6
	Fuse protection for sensors and electronic module	Internal thermal short circuit protection
	Max. current consumption per sensor [A]	0.24
	Max. current consumption of sensor supply, residual current per slave [A]	0.24
	Nominal operating voltage for sensors [V]	24
	Operating voltage range for sensors [V DC]	18 ... 30
	Protection against polarity reversal	For logic and sensor supply and AS-interface
	Electrical separation	
	• between the channels	None
	• to the AS-interface system	None
	Logic level	
	• Signal 0 [V]	≤5
	• Signal 1 [V]	≥-11
	Input delay [ms]	Typically 3
	Switching logic	PNP
	Input characteristic curve	To IEC 1131-2

# AS-interface® components

Compact I/O modules and valve interfaces


FESTO

General technical data		
Type	ASI-8DI-M8-3POL	
General data	Protection class to EN 60529	IP65/IP67 (when fully plugged in or fitted with protective cap)
	Material	Polybuteniterephthalate
	Dimensions (LxWxD)	[mm] 151 x 30 x 30
	Weight	[g] 190
LED displays	Inputs	8 green
	AS-interface LED	Power/green
	FAULT-LED (fault 1, fault 2)	Fault LED/red per slave
AS-interface connection/load voltage connection	Connection with the AS-interface	Via M12 connecting cables, 4-wire
	Watchdog function	Active after 50 ms
	Peripherals fault/diagnostics	Short circuit/overload (thermal fuse on each channel) in accordance with specification c.S.2.1, two red fault LEDs Automatic voltage return
	AS-interface bus voltage	[V] 26.5 ... 31.6
	Total current consumption of AS-interface	[mA] Max. 350
	Current-carrying capacity of M12 pins (AS-i, AUX)	[A] Max. 4
	AS-interface data	
	• IO code	0 <sub>h</sub>
	• ID code 1	A <sub>h</sub>
	• ID code 2	E <sub>h</sub>
	• Profile	S-QA.E
	AS-interface address (factory setting)	#1A, #2A
	AS-interface specification	2.11 (compatible with 3.0)

Operating and environmental conditions		
Type	ASI-8DI-M8-3POL	
Protection class to DIN 60529	IP65/IP67 (when fully plugged-in or fitted with protective cover)	
Ambient temperature	[°C]	-5 ... +50
Storage temperature	[°C]	-20 ... +70
Corrosion resistance class CRC <sup>1)</sup>	1	
CE mark (see declaration of conformity)	To EU EMC Directive <sup>2)</sup>	
	To EU Explosion Protection Directive (ATEX)	
Certification	c UL us - Listed (OL)	

- 1) Corrosion resistance class 1 as per Festo standard 940 070  
Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.
- 2) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: [www.festo.com/sp](http://www.festo.com/sp) → User documentation.  
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

Certifications ATEX		
ATEX category gas	II 3G	
Ex-ignition protection type gas	Ex nA IIC T4 X Gc	
ATEX category dust	II 3D	
EX-ignition protection type dust	Ex tc IIIC T115°C X Dc IP67	
ATEX ambient temperature	[°C]	-5 ≤ Ta ≤ +50

 Note

For the operation of device combinations in hazardous areas, the lowest common zone, temperature class and ambient temperature of the individual devices determine the possible use of the entire module.


# AS-interface® components

Compact I/O modules and valve interfaces



## Connection and display components

### ASI-8DI-M8-3POL



- 1 AS-interface connection, incoming
- 2 Status LED (green)
- 3 Red LED for short circuit/overload display
- 4 Green LED for status display (one LED per input)
- 5 Sensor connections
- 6 AS-interface connection, outgoing

Pin allocation for sensor connections ASI-8DI-M8-3POL					
Pin allocation	Pin	Signal	Description	Pin	Signal
	1	24 V DC	Operating voltage 24 V DC	1	24 V
	3	0 V	Operating voltage 0 V	3	0 V
	4	Ix*	Sensor signal	4	Ix+1*

\* Ix = Input x


# AS-interface® components

Compact I/O modules and valve interfaces

FESTO

## Function

Combined digital input and output modules permit the connection of proximity sensors or other 24 V DC sensors (inductive, capacitive, etc.) as well as up to 3 consuming devices 24 V DC/1 A. The electrical outputs activate actuators such as individual valves, lamps, signal equipment and many more.

 Note  
Optimum actuation for valves with M12 central plug.

Plugs with double allocation are separated using a T-adaptor, DUO plug or DUO cable.

## Applications

- Input/output module for 24 V DC sensor signals and actuators, PNP
- Single slave, contains an AS-interface chip
- M12 plug connection technology, 5-pin, double allocation
- Peripherals fault LED for short circuit/undervoltage of sensors or actuators

- Modules support A/B mode in accordance with Spec. V2.11
- Bus connection 2x M12 for bus in and bus out
- Bus and auxiliary power supply looped through for cascading with further output modules
- Inputs:
  - The input status of each input signal is indicated on an allocated green LED
  - 24 V DC supply for all connected sensors provided via the ("yellow") AS-interface cable
- Outputs:
  - The output status of each output signal is indicated on an allocated yellow LED
  - 24 V DC supply for all connected actuators is provided via the ("black") AS-interface cable



General technical data		
Type		ASI-4DI3DO-M12x2-5POL-Z
Digital inputs	No. of inputs	4
	Power supply 24 V DC	From the AS-interface ("yellow" cable)
	Intrinsic current consumption of electronics [mA]	Typically 35 (inputs not connected)
	Input current at 24 V DC (from sensor) [mA]	Typically 6
	Fuse protection for sensors	Internal thermal short circuit protection
	Max. current consumption per sensor [A]	0.24
	Max. current consumption of sensor supply, residual current per slave [A]	0.25
	Nominal operating voltage for sensors [V]	24
	Operating voltage range for sensors [V DC]	18 ... 30
	Protection against polarity reversal	For logic and sensor supply and AS-interface
	Electrical separation	
	• between the channels	None
	• to the AS-interface system	Yes
	Logic level	
	• Signal 0 [V]	≤ 5
	• Signal 1 [V]	≥ 11
Switching logic	Input delay [ms]	Typically 3
	Switching logic	PNP
	Input characteristic curve	To IEC 1131-2



# AS-interface® components

Compact I/O modules and valve interfaces

FESTO

General technical data		
Type		ASI-4DI3DO-M12x2-5POL-Z
Digital outputs	No. of outputs	3
	Allocation of outputs	Socket 3 with double allocation, socket 4 with single allocation
	Version of the actuator connection	4x M12, 5-pin
	Power supply 24 V DC	From the auxiliary power supply, "black" AS-interface cable
	Max. output current per channel [A]	1.0, 2 outputs can be switched together
	Operating voltage [V DC]	24 ±25%
	Fuse protection for power output	Internal thermal short circuit protection for each output
	Protection against polarity reversal	For actuator supply 24 V/0 V
	Switching logic	PNP
	Output characteristic curve	To ICE 1131-2
	Electrical separation	
	• between the channels	None
	• to the AS-interface system	Yes
	Voltage drop across the output [V]	<1.5
	Limitation of inductive switch-off voltage [V]	-10 ... -45
	LED displays	
General data	• Inputs	4 green
	• Outputs	3 yellow
	• AS-interface LED	Power/green
	• AUX-PWR-LED	Auxiliary power supply/green
	• FAULT-LED	Fault LED/red
General data	Protection class to EN 60529	IP65/IP67 (when fully plugged in or fitted with protective cap)
	Material	Polybuteneterephthalate
	Dimensions (LxWxD) [mm]	151 x 30 x 30
	Weight [g]	165
AS-interface connection/load voltage connection	Connection with the AS-interface	Via M12 connecting cables, 4-wire
	Watchdog function	Active after 50 ms
	Peripherals fault/diagnostics	Short circuit/overload (thermal fuse on each channel) in accordance with specification C.S.2.1, two red fault LEDs Automatic voltage return
	AS-interface bus voltage [V]	26.5 ... 31.6
	Total current consumption of AS-interface [mA]	Max. 250
	Current-carrying capacity of M12 pins (AS-interface, AUX) [A]	Max. 4
	AS-interface data	
	• IO code	7 <sub>h</sub>
	• ID code 1	A <sub>h</sub>
	• ID code 2	2 <sub>h</sub>
	• Profile	S-7.A.2
	AS-interface address (factory setting)	#0A
	AS-interface specification	2.11 (compatible with 3.0)

# AS-interface® components


Compact I/O modules and valve interfaces

FESTO

Operating and environmental conditions		
Type	ASI-4DI3DO-M12x2-5POL-Z	
Protection class to DIN 60529	IP65/IP67 (when fully plugged-in or fitted with protective cover)	
Ambient temperature	[°C]	–5 ... +50
Storage temperature	[°C]	–20 ... +70
Corrosion resistance class CRC <sup>1)</sup>	1	
CE mark (see declaration of conformity)	To EU EMC Directive <sup>2)</sup>	
	To EU Explosion Protection Directive (ATEX)	
Certification	c UL us - Listed (OL)	
Note on materials	Conforms to RoHS	
Paint-wetting impairment substances criterion	PWIS-free	

- 1) Corrosion resistance class 1 as per Festo standard 940 070  
Components requiring low corrosion resistance. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.
- 2) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: [www.festo.com/sp](http://www.festo.com/sp) → User documentation.  
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.


Certifications ATEX		
ATEX category gas	II 3G	
Ex-ignition protection type gas	Ex nA IIC T4 X Gc	
ATEX category dust	II 3D	
EX-ignition protection type dust	Ex tc IIC T115°C X Dc IP67	
ATEX ambient temperature	[°C]	–5 ≤ Ta ≤ +50

 Note


For the operation of device combinations in hazardous areas, the lowest ambient temperature of the individual devices determine the common zone, temperature class and possible use of the entire module.

## Connection and display components


ASI-4DI3DO-M12x2-5POL-Z



- 1 AS-interface connection, incoming
- 2 Status LED (green)
- 3 Green LED for load voltage display
- 4 Green LED for status display (one LED per input)
- 5 Yellow LED for status display (one LED per output)
- 6 Red LED for short circuit/overload display
- 7 AS-interface connection, outgoing
- 8 Sensor connections
- 9 Outputs

Pin allocation for sensor connections ASI-4DI3DO-M12X2-5POL-Z			
Pin allocation	Pin	Signal	Description
	1	24 V DC	Operating voltage 24 V DC
	2	Ix*+1	Sensor signal
	3	0 V	Operating voltage 0 V
	4	Ix*	Sensor signal
	5	Earth	Earth terminal


\* Ix = Input x

Pin allocation for outputs ASI-4DI3DO-M12X2-5POL-Z						
Pin allocation	Outputs 1 and 2			Output 3		
	Pin	Signal	Description	Pin	Signal	Description
	1	n.c.	Not connected	1	n.c.	Not connected
	2	OX*+1	Output	2	n.c.	Not connected
	3	0 V	Operating voltage 0 V	3	0 V	Operating voltage 0 V
	4	OX*	Output	4	OX*+2	Output
	5	Earth	Earth terminal	5	Earth	Earth terminal

\* OX = Output


## Dimensions

ASI-8DI-M8-3POL



Download CAD data → [www.festo.com](http://www.festo.com)











ASI-4DI3DO-M12x2-5POL-Z



## AS-interface® components

Compact I/O modules and valve interfaces – Accessories












**FESTO**

Ordering data				
Description			Part No.	Type
Bus connection				
	AS-interface flat cable, yellow	100 m	18940	KASI-1,5-Y-100
	AS-interface flat cable, black	100 m	18941	KASI-1,5-Z-100
	Cable cap for flat cable (scope of delivery 50 pieces)		18787	ASI-KK-FK
	Cable sleeve (scope of delivery 20 pieces)		165593	ASI-KT-FK
	Socket M12, 4-pin	For AS-interface flat cable	18789	ASI-SD-PG-M12
Cable distributor				
	AS-Interface data to socket M12, 4-pin		572225	NEFU-X22F-M12G4
	AS-Interface data and load voltage supply to socket M12, 4-pin		572226	NEFU-X24F-M12G4
	AS-Interface data and load voltage supply to socket M12, 4-pin, cable length 1 m		572227	NEFU-X24F-1-M12G4
T-type plug connector				
	T-adapter for DH-485, M12 5-pin		171175	FB-TA-M12-5POL
	Plug M12, A-coded, 4-pin	2x socket M12, A-coded, 5-pin	8005310	NEDY-L2R1-V1-M12G5-N-M12G4
		2x socket M8, A-coded, 3-pin	8005311	NEDY-L2R1-V1-M8G3-N-M12G4
	Modular system for sensor/actuator distributor ➔ Internet: nedy		–	NEDY-...

## AS-interface® components

Compact I/O modules and valve interfaces – Accessories






**FESTO**

Ordering data				
	Description		Part No.	Type
Connecting cables				
	Modular system for connecting cables ➔ Internet: nebu		–	NEBU-...
	Straight plug M8, 3-pin, straight socket M8, 3-pin	0.5 m	541346	NEBU-M8G3-K-0.5-M8G3
		1.0 m	541347	NEBU-M8G3-K-1-M8G3
		2.5 m	541348	NEBU-M8G3-K-2.5-M8G3
		5.0 m	541349	NEBU-M8G3-K-5-M8G3
Straight plug M12, 4-pin, straight socket M12, 5-pin	0.5 m	8000208	NEBU-M12G5-K-0.5-M12G4	
DUO plugs				
	Plug M12 for 2 sensor cables	4-pin, PG11	18779	SEA-GS-11-DUO
		5-pin, PG11	192010	SEA-5GS-11-DUO
Sensor plugs				
	Straight sensor plug	M12, 5-pin, PG7	175487	SEA-M12-5GS-PG7
	Straight sensor plug	M12, 4-pin, PG7	18666	SEA-GS-7
	Straight sensor plug	M12, PG9, 4-pin	18778	SEA-GS-9
	Straight sensor plug for cable Ø 2.5 mm	M12, 4-pin	192008	SEA-4GS-7-2,5
	Straight sensor plug	M8, screw-in, 3-pin	192009	SEA-3GS-M8-S
	Straight sensor plug	M8, solderable, 3-pin	18696	SEA-GS-M8
	Cover cap (scope of delivery 10 pieces)	M12	165592	ISK-M12
		M8	177672	ISK-M8
Miscellaneous				
	Primary switched mode, modular power supply 24 V DC power supply	5 A	2247681	CACN-3A-1-5
		10 A	2247682	CACN-3A-1-10
	Addressing device (power supply plug included in scope of delivery)		18959	ASI-PRG-ADR
	Addressing cable		18960	KASI-ADR

## AS-interface® components

Compact I/O modules and valve interfaces – Accessories

**FESTO**

Ordering data			
	Description	Part No.	Type
I/O modules			
	AS-interface input module for 8 inputs M8	542124	ASI-8DI-M8-3POL
	AS-interface input/output module for 4 inputs/3 outputs M12	542125	ASI-4DI3DO-M12X2-5POL-Z
Mountings			
	H-rail to EN 60715	35430	NRH-35-2000
	Mounting for H-rail	170169	CP-TS-HS35
Inscription labels			
	Inscription labels 8x20 mm in frames (20 pieces)	539388	IBS-8x20

# AS-Interface® components

Addressing device

FESTO

## Addressing device ASI-PRG-ADR

- Parameterisation of AS-Interface components
- Display and editing of addresses, input and output signals
- Corresponds to AS-Interface SPEC 3.0



### Description

Before an AS-Interface network is commissioned, addresses must be assigned to the connected slaves. These addresses are stored in an EEPROM chip on each slave. Each slave is connected to the addressing device for the allocation of an address. Addressing is simple and is carried out using 5 keys.

The main advantages are:

- Compact design
- Can be addressed on-site
- Supports AS-Interface specification S-7.7.A.7 (SPEC 3.0), S-QB and S-7.B (AS-Interface Safety at Work)

Using the addressing device according to SPEC 3.0, it is possible to scan the AS-Interface from any chosen point in the network. At all connected stations

- slave addresses can be read/changed
- ID and IO codes can be read out
- parameters can be read/changed
- input/output data can be read and written (setting outputs)
- error messages can be read out and quickly recognised

Independent of voltage supplies

- Battery operation

Simple reading of error codes

- LCD display

Reliable

- Short-circuit proof
- Overload-proof

Universal adapter connection suitable for a large number of AS-Interface slaves. Additional addressing cable for slaves with M12 round plug or flat-cable socket optionally available.

### General technical data

Display	LCD display
Control elements	Membrane keypad
	5 keys
No. of function keys	5
Dimensions W x L x H [mm]	34 x 210 x 80
Product weight [g]	610

### Technical data – Electrical

Nominal operating voltage [V DC]	28
Permissible load current [mA]	100
Power supply	Lithium battery
Short circuit protection	Yes
Overload protection	Present

### Technical data – Fieldbus interface

Protocol	AS-Interface SPEC 3.0
Connection type	Socket
Connection technology	M12x1, A-coded
Number of pins/wires	5
Based on standard	To EN 61076-2-101

# AS-Interface® components

Addressing device



Materials	
Housing	PA reinforced
Note on materials	RoHS compliant

Operating and environmental conditions	
Ambient temperature [°C]	0 ... +40
Degree of protection	IP20
CE marking (see declaration of conformity) <sup>2)</sup>	To EU EMC Directive <sup>1)</sup>

- 1) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: [www.festo.com/sp](http://www.festo.com/sp) → User documentation.  
 If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.
- 2) Additional information [www.festo.com/sp](http://www.festo.com/sp) → Certificates.



Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

1

LCD display, character height 13 mm

	B1	H1	H2	L1	L2
ASI-PRG-ADR	34	210	35	80	43

Ordering data			
	Designation	Part No.	Type
	Addressing device	18959	ASI-PRG-ADR
	Addressing cable	18960	KASI-ADR




# AS-interface® components

Accessories

FESTO

## Overview of cables

### Addressing cable – KASI-ADR




The addressing cable ASI-ADR, available as an accessory, can be used to address any desired slaves either

directly via the flat cable connection (FK) or via the M12 connection (M12):

- Individual valve interface (FK)

- Compact I/O modules (M12)
- CPV valve terminals (FK)
- SPC11 Soft Stop (FK)

### Flat cable – KASI-1,5-...-100




KASI-1,5-Y-100 (yellow)  
KASI-1,5-Z-100 (black)

The flat cable is of a 2-wire design. The coding profile prevents polarity reversal of the cable.

AS-interface network stations are connected to the flat cable via insulation displacement technology which utilises contact pins, thus eliminating the need to strip cable and wire insulation.

The yellow cable is normally used for the AS-interface network and the black cable for the auxiliary power supply.

### Connecting cable NEBU-M12...-M12...



The round cables are of a 4-wire design and are protected against polarity reversal. Standardised connection technology replaces the yellow/black AS-interface cable with a common cable.

- Fixed lengths: 0.2 m, 1 m, 2.5 m and 5 m ex-stock
- NEBU modular system for connecting cables



#### Note

Define your connecting cable yourself. Select M8 (3-pin or 4-pin) or M12 (4-pin or 5-pin) on each side as required and specify the required cable length and quality – Festo will then supply the exact cable you require.

→ [www.festo.com](http://www.festo.com)


### Flat cable sleeve – ASI-KT-FK



For insulating and sealing the AS-interface cable at the end of the string

- Protection class IP65
- Shrinks on application of heat (hot air blower etc.)

### Cable cap – ASI-KK-FK




For insulating and sealing the AS-interface cable at the end of the string

- Protection class IP65

## Dimensions


Download CAD data → [www.festo.com](http://www.festo.com)

### Addressing cable – KASI-ADR




- 1 Round plug connector for connection to addressing device
- 2 Flat cable socket for connecting stations in the AS-interface network with plug-in connection
- 3 Flat cable socket with M12 connection plug for stations in the AS-interface network with M12 interface

### Flat cable – KASI-1,5-...-100




- 1 blue (-)
- 2 brown (+)

### Flat cable sleeve – ASI-KT-FK



### Cable cap – ASI-KK-FK




## Overview of connection components

### Flat cable socket


Flat cable socket for connecting AS-interface network stations to the flat cable. The connection is detachable.

The cable socket is protected against reverse polarity.




#### ASI-SD-FK

Flat cable socket for CPV valve terminals.




#### ASI-SD-FK180

Version FK180 for looping through of flat cable on top.



#### ASI-SD-FK-M12


Blanking plug for sealing unused connections for flat cable sockets.



#### ASI-SD-PG-M12


Flat cable socket with M12 connection and special seal for the flat cable in a PG connector. For compact input module (ASI-8DI-M8-3POL).

### Flat cable distributors



#### ASI-KVT-FK


Parallel flat cable distributor enables the flat cable to be branched at any desired point to the AS-interface network stations.



#### ASI-KVT-FK-S

Symmetrical flat cable distributor that enables the coding profile of the flat cable to be turned through 180° when changing cables. This avoids the need to install a loop. Three cable caps are provided in the scope of delivery to seal the cable ends.

### Cable distributor




#### NEFU-X2

Flat cable socket with M12 connection for looping through the flat cable.

Can be plugged into 4-pin and 5-pin interfaces.

## Overview – Distributor


### T-type plug connector – NEDY



The sensor/actuator distributors combine two sensor signals (2x 3-pin cable) on one 4-pin plug. This is routed to the 4-pin or 5-pin input socket of a valve terminal or the

compact I/O module. Variants and cable lengths can be configured:  
➔ Internet: nedy


### DUO plug – SEA-5GS11-DUO



The DUO plug combines two sensor or actuator signals/cables in one housing.

## Overview – Other connecting cables

### Extension cable – NEBU




The connecting cables can be used to extend the cable length between a distributor and the inputs of a valve terminal or a compact I/O module.

They can also be used as AS-interface bus cables for M12 connection technology.

Variants and cable lengths can be configured:  
➔ Internet: nebu

## Overview – Other accessories


### Inscription labels IBS-...



Convenient labelling system for

- flat cable sockets
- flat cable distributors
- individual valve interfaces
- compact I/O modules
- CPV valve terminals

### H-rail NRH-35-2000
















- For compact I/O modules
- CPV valve terminals
- For individual valve interfaces
- AS-interface power supply units












# AS-interface® components

Accessories

**FESTO**

Ordering data				
	Description		Part No.	Type
Bus connection				
	AS-interface flat cable, yellow	100 m	18940	KASI-1,5-Y-100
	AS-interface flat cable, black	100 m	18941	KASI-1,5-Z-100
	Flat cable socket		18785	ASI-SD-FK
	Flat cable socket	Turned through 180°	196089	ASI-SD-FK180
	Flat cable blanking plug		196090	ASI-SD-FK-BL
	AS-interface flat cable distributor	Parallel cable	18786	ASI-KVT-FK
	AS-interface flat cable distributor	Symmetrical cable	18797	ASI-KVT-FK-S
	Cable cap for flat cable (scope of delivery 50 pieces)		18787	ASI-KK-FK
	Cable sleeve (scope of delivery 20 pieces)		165593	ASI-KT-FK
	Socket M12, 4-pin	For AS-interface flat cable	18789	ASI-SD-PG-M12
	Socket M12, 5-pin	For round cable	18324	FBSD-GD-9-5POL
Cable distributor				
	AS-Interface data to socket M12, 4-pin		572225	NEFU-X22F-M12G4
	AS-Interface data and load voltage supply to socket M12, 4-pin		572226	NEFU-X24F-M12G4
	AS-Interface data and load voltage supply to socket M12, 4-pin, cable length 1 m		572227	NEFU-X24F-1-M12G4

Ordering data				
	Description		Part No.	Type
Sensor plugs				
	Straight sensor plug	M12, 5-pin, PG7	175487	SEA-M12-5GS-PG7
	Straight sensor plug	M12, 4-pin, PG7	18666	SEA-GS-7
		M12, PG9, 4-pin	18778	SEA-GS-9
	Angled sensor plug	M12, 4-pin	12956	SIE-WD-TR
	Straight sensor plug for cable Ø 2.5 mm	M12, 4-pin	192008	SEA-4GS-7-2,5
	Straight sensor plug	M8, screw-in, 3-pin	192009	SEA-3GS-M8-S
	Straight sensor plug	M8, solderable, 3-pin	18696	SEA-GS-M8
	Harax sensor plug	4-pin	525928	SEA-GS-HAR-4POL
	Sub-D plug	25-pin	527522	SD-SUB-D-ST25
	Cover cap (scope of delivery 10 pieces)	M12	165592	ISK-M12
		M8	177672	ISK-M8
DUO plugs				
	Plug M12 for 2 sensor cables	4-pin, PG11	18779	SEA-GS-11-DUO
		5-pin, PG11	192010	SEA-5GS-11-DUO
T-type plug connector				
	T-adaptor for DH-485, M12 5-pin		171175	FB-TA-M12-5POL
	Plug M12, A-coded, 4-pin	2x socket M12, A-coded, 5-pin	8005310	NEDY-L2R1-V1-M12G5-N-M12G4
		2x socket M8, A-coded, 3-pin	8005311	NEDY-L2R1-V1-M8G3-N-M12G4
	Modular system for sensor/actuator distributor ➔ Internet: nedy		–	NEDY-...

Ordering data				
	Description		Part No.	Type
Connecting cables				
	Modular system for connecting cables ➔ Internet: nebu		–	NEBU-...
	Straight plug M8, 3-pin, straight socket M8, 3-pin	0.5 m	541346	NEBU-M8G3-K-0.5-M8G3
		1.0 m	541347	NEBU-M8G3-K-1-M8G3
		2.5 m	541348	NEBU-M8G3-K-2.5-M8G3
		5.0 m	541349	NEBU-M8G3-K-5-M8G3
	Straight plug M12, 4-pin, straight socket M12, 5-pin	0.5 m	8000208	NEBU-M12G5-K-0.5-M12G4
	Connecting cable, straight plug, straight socket	M12, 8-pin, 2.0 m	525617	KM12-8GD8GS-2-PU
Miscellaneous				
	Primary switched mode, modular power supply 24 V DC power supply	5 A	2247681	CACN-3A-1-5
		10 A	2247682	CACN-3A-1-10
	Addressing device		18959	ASI-PRG-ADR
	Addressing cable		18960	KASI-ADR
Inscription labels				
	Inscription labels in frames	8x20 mm (20 pieces)	539388	IBS-8x20
		6x10 mm (64 pieces)	18576	IBS-6x10
		9x20 mm (20 pieces)	18182	IBS-9x20
	For foil Inscription label holder for sub-base, transparent, for paper foil label	can be used for VMPA1 VMPA2	533362	VMPA1-ST-1-4
		can be used for VMPA14	8085996	VMPA14-ST-1-4
	For IBS Inscription label holder for sub-base, 4-fold, for IBS-6x10	can be used for VMPA1 VMPA2	544384	VMPA1-ST-2-4
		can be used for VMPA14	8085997	VMPA14-ST-2-4
Mounting accessories				
	Mounting for H-rail		170169	CP-TS-HS35
	Mounting for H-rail		526032	CPX-CPA-BG-NRH
	H-rail to EN 60715		35430	NRH-35-2000
	Mounting bracket		534416	VMPA-BG-RW

## Festo - Your Partner in Automation



**1 Festo Inc.**  
5300 Explorer Drive  
Mississauga, ON L4W 5G4  
Canada

### Festo Customer Interaction Center

Tel: 1 877 463 3786  
Fax: 1 877 393 3786  
Email: [customer.service.ca@festo.com](mailto:customer.service.ca@festo.com)



**2 Festo Pneumatic**  
Av. Ceylán 3,  
Col. Tequesquináhuac  
54020 Tlalneantla,  
Estado de México

### Multinational Contact Center

01 800 337 8669  
[ventas.mexico@festo.com](mailto:ventas.mexico@festo.com)



**3 Festo Corporation**  
1377 Motor Parkway  
Suite 310  
Islandia, NY 11749

### Festo Customer Interaction Center

1 800 993 3786  
1 800 963 3786  
[customer.service.us@festo.com](mailto:customer.service.us@festo.com)



**4 Regional Service Center**  
7777 Columbia Road  
Mason, OH 45040

### Connect with us



[www.festo.com/socialmedia](http://www.festo.com/socialmedia)



[www.festo.com](http://www.festo.com)

Subject to change