



Key features

#### Overview

- - -

The products optimise the use of compressed air as an energy medium in industrial automation technology. They are with measurement, control and diagnostic functions and support energy-efficient operation of pneumatic systems. In automatic operation, they detect standby states of the production system and shut off the compressed air feed until it is reset by the user; the shut-off is either permanent (MSE6-D2M and MSE6-E2M) or until the pressure drops to the setpoint standby pressure, which is then maintained (MSE6-C2M). This prevents unnecessary and/or increased consumption of compressed air. By monitoring the pressure drop in the shut-off state, it is possible to detect leakages and introduce specific system maintenance actions.

The products can also be used for process monitoring by enabling pressure, flow-rate and consumption values to be transferred by a fieldbus connection directly to the machine controller, where they can be analysed. These data can be transferred to the cloud, for example via the Festo IO-Gateway, so that they can be recorded and analysed over long periods of time. The range of different equipment and functions of the three product variants are shown in the following table.

Product features			
Туре	MSE6-C2M	MSE6-D2M	MSE6-E2M
Control function (energy efficiency function)	<ul> <li>For regulating to the adjustable normal setpoint pressure as well as automatic shut-off and subsequent regulation to the adjustable setpoint standby pressure if the flow rate drops below the limit value for a prolonged period</li> <li>User-controlled shut-off and pressure regulation</li> <li>Parameterisable up-rate limit for setpoint pressure</li> </ul>	<ul> <li>Automatic shut-off if the flow rate drops below the limit value for a prolonged period</li> <li>User-controlled shut-off and pressurisation</li> </ul>	<ul> <li>Automatic shut-off if the flow rate drops below the limit value for a prolonged period</li> <li>User-controlled shut-off and pressurisation</li> </ul>
Recording and provision of measurement data	<ul> <li>Output pressure</li> <li>Pressure change (for monitoring pressure-tightness)</li> <li>Flow rate</li> <li>Air consumption</li> </ul>	<ul> <li>Output pressure</li> <li>Pressure change (for monitoring pressure-tightness)</li> <li>Flow rate</li> <li>Air consumption</li> </ul>	<ul> <li>Output pressure</li> <li>Pressure change (for monitoring pressure-tightness)</li> <li>Flow rate</li> <li>Air consumption</li> </ul>
Limit monitoring	<ul> <li>Pressure, lower and upper limit value</li> <li>Pressure change in shut-off mode, upper limit value</li> <li>Flow rate, upper limit value</li> </ul>	<ul> <li>Pressure, lower and upper limit value</li> <li>Pressure change in shut-off mode, upper limit value</li> <li>Flow rate, upper limit value</li> </ul>	<ul> <li>Pressure, upper limit value</li> <li>Pressure change in shut-off mode, upper limit value</li> <li>Flow rate, upper limit value</li> </ul>
Electrical inputs/outputs	<ul> <li>2 digital inputs</li> <li>2 digital outputs</li> <li>Channel-based status indicator via LED</li> <li>Parameterisable special functions</li> </ul>	-	-
Fieldbus connection	<ul> <li>PROFINET IO via integrated fieldbus node</li> </ul>	<ul> <li>PROFINET IO via the fieldbus node of the CPX terminal or MSE6-C2MM actuated via a CPX extension</li> </ul>	<ul> <li>PROFIBUS DP via integrated fieldbus node</li> <li>PROFINET IO via integrated fieldbus node</li> <li>EtherNet/IP via integrated fieldbus node</li> <li>EtherCAT via integrated fieldbus node</li> </ul>
System extension/integration	CPX extension interface row 1 for connecting a MSE6-D2M or connecting digital and analogue CPX IO modules (MSE6-C2MM only)	CPX extension interface row 2 for connection to a MSE6-C2MM or to a CPX terminal with CPX extension interface row 1	-

Key features

#### Functions

Standby detection, automatic shut-off and regulation of compressed air supply (MSE6-C2M only)

If parameterised accordingly, the product detects when a pneumatic system is at a standstill. The system is separated from the compressed air supply using the shut-off valve without exhausting the downstream system. This avoids additional air consumption through leakages. The product remains shut-off until the output pressure has dropped to the

output pressure has dropped to the parameterisable setpoint standby pressure. The shut-off valve is then

Manual switching on/off of the compressed air supply

The automatic shut-off and regulation of the compressed air supply can be activated and deactivated by the user. Deactivation is worthwhile during commissioning or a critical production process if automatic standby detection is difficult or not possible. This allows the shut-off valve and pressure regulator to be directly and remotely controlled by the machine controller. Moreover, the MSE6 of the PLC can issue a "shut-off recommendation" in semi-automatic mode. The PLC program then decides whether to switch to standby mode or not.

The product continuously records the

flow rate, prepares the data and

makes them available cyclically.

To detect excessive flow rates, the

product offers the option of paramet-

erising the upper limit value for the

flow rate. If the parameterised limit

value is exceeded, the product will

output a diagnostic message.

re-opened and this pressure value is

maintained. This prevents the system

from being exhausted unnecessarily

and enables leaks to be detected by

If the product receives a release signal

off/regulation mode, the shut-off valve

in the automatically activated shut-

opens, and the pressure regulator

switches back to normal pressure

regulation.

Flow recording

analysing the pressure drop.

#### Pressure recording

The product continuously records the output pressure, prepares the data and makes them available cyclically. To detect operating pressures that are too high or too low (MSE6-C2M/D2M only), the product offers the option of parameterising limit values for pressure. If the parameterised limit value is exceeded, the device will output a diagnostic message.

## - 🗍 - Note

If there is an error (e.g. fieldbus interruption, PLC failure, no voltage) on the MSE6-D2M/E2M, then the shut-off valve switches to the initial position (pressurise) if the system parameters are set accordingly. If the valve was previously shut off, the system is pressurised. If the system was exhausted, pressurisation takes place suddenly.

Use suitable counter measures to prevent unintentional pressurisation of the system in the event of an error.

# Standby detection and automatic shut-off of compressed air supply (MSE6-D2M/E2M only)

If parameterised accordingly, the product detects when a pneumatic system is at a standstill. The system is separated from the compressed air supply using the shut-off valve without exhausting the downstream system. This avoids additional air consumption through leakages. If the product receives a release signal in the automatically activated shut-off mode, the shut-off valve opens, and the system is again supplied with compressed air. After exhausting via port 1, a residual pressure of < 1 bar can remain at port 2.

#### Testing pressure-tightness

In the shut-off state, the product measures the pressure change over time.

Even in well-serviced systems, the pressure falls continuously due to leakages. The fewer leakages the

system has, the slower the pressure drop will be. The measured pressure change is indicative of leakages in the system. If the parameterised limit value is exceeded, the device will output a diagnostic message.

#### Consumption recording

The product determines the compressed air consumption by recording the flow rate. With the aid of output data, the consumption measurement can be switched on and off and the consumption value can be reset.

## -O- New MSE6-C2M/D2M

#### 2019/05 - Subject to change

Key features

#### CPX extension (MSE6-C2M-...-M and MSE6-D2M only)

The MSE6-C2M-...-M can be extended with a MSE6-D2M using the CPX interface. This combination allows for energy efficiency functions on two separate compressed air systems, activated via a common bus node. As an alternative to the MSE6-D2M, CPX IO modules can also be connected to a MSE6-C2M-...-M. A CPX terminal can also be used to activate the

### MSE6-D2M instead of the

MSE6-C2M-...-M. The CPX extension can be flexibly mounted on two levels (rows) situated one above the other, making it particularly suitable for tight installation conditions, e.g. in a control cabinet. For further information, please see the technical data for these modules on the following pages.



FESTO

#### Combination of service unit components from series MS6 and MSE6

Additional service unit components of the MS6 series can be connected to the left and right of an MSE6. With this combination, the following points should be noted:

- A maximum of 10 individual devices are permitted. The MSE6-C2M counts as three devices.
- Only use the wall mounting SET MS6-WPG and module connector MS6-MV-EX. Fit a wall mounting SET MS6-WPG after every second service unit component.
- No division of modules within the MSE6.
- Remove the left connecting plate from the MSE6 and mount on the extension on the left. Do the same in the case of an extension on the right (see dashed arrows).
- Connect the earth terminal on the left-hand connecting plate to the end plate of the electrical interlinking module of the MSE6. A longer FE connection may be required.



- Left end plate of the electrical 2 interlinking module of the MSE6-C2M with earth terminal
- 5 On/off valve MS6-EM1 Module connector MS6-MV-EX
- 6 7 Left connecting plate
- 10 Right connecting plate

-©- New MSE6-C2M/D2M

## Energy efficiency modules MSE6, MSE series

Key features

#### FESTO

#### Design

MSE6-C2M

The main components of the product are: fieldbus node, flow sensor, proportional-pressure regulator and shut-off valve with pressure sensor. The fieldbus interface allows connection to a higher-order controller, e.g. a system or machine controller. Certain devices, such as the MSE6-D2M or CPX IO modules, can be connected to the CPX extension connection row 2 via the CPX extension connection row 1.



#### MSE6-D2M

The main components of the product are: flow sensor and shut-off valve with pressure sensor. It has a CPX extension connection row 2 for connection to a decentralised, separate fieldbus node with CPX extension connection row 1, e.g. MSE6-C2M-...-M or CPX terminal.



#### MSE6-E2M

The main components of the MSE6-E2M are: shut-off valve, flow sensor, pressure sensor and bus node. The fieldbus interface allows connection to a higher-order controller, e.g. a system or machine controller.



# Energy efficiency modules MSE6-C2M/D2M, MSE series Peripherals overview



Acce	ssories		→ Page/Internet
1	Energy efficiency module		8
	MSE6-C2M		
2	Energy efficiency module		14
	MSE6-D2M		
3	Power supply socket	30	
	NECU-M-PP		
4	Plug	For fieldbus node FB34 for PROFINET IO	30
	FBS-RJ45		
5	Connecting cable	For CPX extension (MSE6-C2MM only)	30
	NEBC-F12G8		
6	Connecting cable	For electrical inputs/outputs	31
	NEBU-M12		
7	Wall mounting SET	For same wall gap for combining series MS6 and MSE6	31
	MS6-WPG		
8	Module connector	For connecting modules	31
	MS6-MV-EX		
9	Silencer	For noise reduction	31
	U		

		MSE	6	- C2M	] - [	5000	- FB34	÷ -	D	- M	– RG	– BAR	– AMI	– AGD
Series														
MSE	Modular standard electric													
MJL	Modular standard, electric													
Size														
6	Grid dimension 62 mm			J										
L														
Functio	n													
C2M	Energy efficiency module													
D2M	Energy efficiency module													
Flow me	easuring range													
5000	5000 l/min													
Electrica	al actuation													
CBUS	Internal electrical activation													
FB34	Fieldbus node for PROFINET IO with RJ45 por	t												
<b>F1</b>														
Electrica														
<b>D</b>	No digital inputs/outputs													
D	2 digital inputs, 2 digital outputs													
Electrica	al system extension													
	No CPX extension connection										1			
Μ	CPX extension connection row 1 (master)													
S	CPX extension connection row 2 (slave)													
Measur	ed value display													
RG	Integrated pressure gauge with red/green sca	ale												
-														
Pressur	e gauge scale												J	
BAR	bar													
Electrica	al connection													
AMI	Operating voltage plug push-pull, AIDA													J
VCB	Power supply via C-bus													
	·····	]												
Pneuma	tic connection													
AGD	Connecting plate G <sup>1</sup> /2													

Technical data – Fieldbus node FB34 for PROFINET IO

#### MSE6-C2M-...-FB34

- Consisting of
- Fieldbus node for PROFINET IO
- Flow sensor
- Proportional-pressure regulator
- Shut-off valve with pressure sensor and pressure gauge
- CPX extension connection row 1 (master)
- Electrical inputs/outputs



Temperature range
 0 ... +50 °C





#### Key features

The MSE6-C2M is an intelligent combination of proportional-pressure regulator, on/off valve, sensors and fieldbus communication. It monitors the flow rate and, when production is not taking place, it automatically shuts off after a defined idle time. At the same time, it prevents the system pressure from falling below a defined standby pressure level. The lower pressure level saves energy, without completely depressurising the system. This results in energy savings without affecting the availability of the machine/system.

The MSE6-C2M can automatically detect leakages occurring over time and reports these to a controller. It can be fully integrated into the machine network via PROFINET IO. All measured values (pressure, flow rate, consumption, system parameters) are available in the PLC/cloud and can be displayed or individually further processed. The PLC can also be used to activate the two integrated digital inputs and outputs. Via the CPX extension (MSE6-C2M-...-M only), there is the option of connecting a MSE6-D2M or CPX IO modules.

- Adjustable, regulated output pressure
- Automatic detection of system downtime using flow measurement
- Automatic pressure reduction without exhausting the system by regulating the standby pressure during downtimes
- Leakage detection by evaluating the pressure drop in standby operation

#### 📲 - Note

Pressure zones that may not be shut off or reduced must be branched off upstream of the MSE6-C2M. A signal from the PLC is required for a restart after shut-down or standby. There is no automatic restart for safety reasons.

- Adjustable pressure up-rate limit
- Digital inputs/outputs
- Direct activation/integration of 2 digital inputs (2DI) and 2 digital outputs (2DO), e.g. for valve actuation or for the sensors
- Can be extended within the CPX system via CPX extensions



·O· New

### Energy efficiency modules MSE6-C2M, MSE series

Technical data – Fieldbus node FB34 for PROFINET IO

#### **CPX** extension

Extension with MSE6-D2M



- Energy efficiency function for two separate compressed air systems
  Leakage detection
- Connection to MSE6-C2M-...-M with
- CPX extensionOnly one fieldbus connection
- required
- Process monitoring
- Integrated pressure, flow rate and consumption measurement
- Fieldbus-controlled pressure regulation with automatic standby pressure reduction (MSE6-C2M only)

FESTO

 Direct activation/integration of 2 digital inputs (2DI) and 2 digital outputs (2DO), e.g. for valve actuation or for the sensors (MSE6-C2M only)

Extension with up to 3 CPX IO modules



- Optional integration of additional digital/analogue inputs/outputs with CPX IO modules (up to 3 modules). The following electronics modules are supported → See following table
- Energy efficiency function with pressure regulation
- Leakage detection
- Only one fieldbus connection required
- Process monitoring with leakage detection

- Integrated pressure, flow rate and consumption measurement
- Fieldbus-controlled pressure regulation with automatic standby pressure reduction
- Direct activation/integration of 2 digital inputs (2DI) and 2 digital outputs (2DO), e.g. for valve actuation or for the sensors

# - 闄 - Note

A CPX IO module consists of the electronics module, an interlinking block and a connection block. There are several selected options available. The possible combinations of these modules as well as information and ordering data for additional accessories (end plate with CPX extension, tie rod and mounting accessories) can be found in the CPX documentation.

➔ Internet: cpx

Electronics modules							
Description	Part no.	Туре					
Input modules, digital							
4 digital inputs, 24 V DC, PNP	195752	CPX-4DE					
8 digital inputs, 24 V DC, PNP	195750	CPX-8DE					
Output modules, digital							
4 digital outputs, 24 V DC, 1.0 A, PNP	195754	CPX-4DA					
8 digital outputs, 24 V DC, 0.5 A, PNP	541482	CPX-8DA					
Input/output modules, digital							
8 digital inputs, 8 digital outputs, 0.25 A, PNP	526257	CPX-8DE-8DA					
Analogue modules							
4 analogue current and voltage inputs:	573710	CPX-4AE-U-I					
±10 V, ±5 V, 0 10 V, 1 5 V, ±20 mA, 0 20 mA, 4 20 mA							
2 analogue current and voltage outputs:	526170	CPX-2AA-U-I					
0 10 V, 0 20 mA, 4 20 mA							

### **FESTO**

General technical data		
Pneumatic port 1, 2		G <sup>1</sup> /2 (connecting plate)
Mounting position		Horizontal ±5°
Flow direction		Unidirectional P1 $\rightarrow$ P2
Valve function		2/2-way shut-off valve, open, monostable
Pressure regulation range	[bar]	2.5 10
Max. pressure hysteresis	[bar]	0.3
Reset method		Mechanical
Electrical data		
System supply		
Electrical connection		5-pin, push-pull, AIDA
Operating voltage range for	[V DC]	21.6 28.8
load voltage		
Operating voltage range for	[V DC]	18 30
electronics/sensors		
Current consumption for	[mA]	Max. 260 <sup>1)</sup> when valve is supplied with current and electric pressure regulation is active
actuator technology		
Current consumption for	[mA]	Max. 370 <sup>2)</sup>
electronics/sensors at 24 V		
Reverse polarity protection		For operating voltage connections
Degree of protection		IP65 with plug socket
Duty cycle	[%]	100
Inputs/outputs		
No. of inputs/outputs		2
Switching logic inputs/outputs		PNP (positive switching)
Load capacity per output	[A]	Max. 1 (12 W lamp load) in compliance with the permitted total current from both outputs of max. 1 A
Fieldbus connection		
Fieldbus interface		2x RJ45 push-pull socket, AIDA

Plus max. 1000 mA (max. load current for electrical outputs)
 Plus max. 1000 mA (max. available sensor supply current at electrical inputs)

Standard nominal flow rate qnN <sup>1)</sup>	
Pneumatic connection	G <sup>1</sup> /2
In main direction of flow [l/min]	7000
$1 \rightarrow 2$	

1) Measured at p1 = 10 bar and p2 = 6 bar,  $\Delta p = 1$  bar

Operating and environmental conditions									
Operating pressure	[bar]	511							
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]							
Note on operating/		Lubricated operation not possible							
pilot medium									
Ambient temperature	[°C]	0 +50							
Temperature of medium	[°C]	0 +50							
Storage temperature	[°C]	-10 +60							
Corrosion resistance class CRC	1)	2							
CE mark (see declaration of co	nformity)	To EU EMC Directive <sup>2)</sup>							
Certification		RCM compliance mark							

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmo-sphere typical for industrial applications.

For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com/sp > User documentation.

If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

#### Display/operation

Flow measurement		
Flow measuring range start	[l/min]	50
value		
Flow measuring range end	[l/min]	5000
value		
Accuracy of flow rate		+/- (3% of measured value + 0.3% FS) <sup>1)</sup>
Displayable unit(s)		l/min (preset)
		scfm
Pressure measurement		
Pressure measuring range	[bar]	0
start value		
Pressure measuring range end	[bar]	14
value		
Accuracy in ±%FS <sup>1)</sup>	[%FS]	3
Displayable unit(s)		mbar (preset)
		kPa
		psi
Consumption measurement		
Displayable unit(s)		l (preset)
		m <sup>3</sup>
		scf

1) % FS = % of measuring range end value (full scale)

Weight									
Product weight	[g]	4550							

Materials
-----------

Housing	Die-cast aluminium
Сар	Reinforced PA
Cover	Reinforced PA
Seals	NBR

Pin allocation, system supply			
RJ45 push-pull socket, AIDA	Pin	Function	
54321	1	24 V DC	Operating voltage supply for electronics/sensors U <sub>EL/SEN</sub>
	2	0 V	Operating voltage for electronics/sensors U <sub>EL/SEN</sub>
	3	24 V DC	Load voltage supply for actuators U <sub>OUT/A</sub>
	4	0 V	Load voltage for actuators U <sub>OUT/A</sub>
	5	FE	Functional earth

#### Electrical connection example



- 1 MSE6-C2M-...(-M)
  - 2 Equipotential bonding between the earth terminal of the left pneumatic connecting plate and the left end plate of the electrical interlinking module

- 3 Equipotential bonding for functional earth (FE)
- 4 System supply
- 5 CPX extension connection row 1 (MSE6-C2M-...-M only)
- 6 External fuse
- 7 Supply for actuators can be shut down separately
- 8 MSE6-D2M

Pin allocation for inputs/outputs							
Plug M12x1, 5-pin	Pin	Function					
2	Electrical inputs						
	1	24 V DC	Supply voltage				
10003	2	Input-1	Input 1				
	3	0 V	Load				
5' 4	4	Input-0	Input 0				
4	5	FE	Functional earth				
	Electrical outputs						
	1	-	Not assigned				
	2	Output-1	Output 1				
	3	0 V	Load				
	4	Output-0	Output 0				
	5	FE	Functional earth				

### FESTO



Fieldbus node FB34 for PROFINET IO with RJ45 port

Fieldbus node FB34 for PROFINET IO with RJ45 port

MSE6

MSE6

With CPX extension

G1⁄2

G1⁄2

8085455

8085454

MSE6-C2M-5000-FB34-D-RG-BAR-AMI-AGD

MSE6-C2M-5000-FB34-D-M-RG-BAR-AMI-AGD

#### FESTO

Technical data

#### MSE6-D2M

- Consisting of
- Flow sensor
- Shut-off valve with pressure sensor and pressure gauge
- CPX extension connection row 2 (slave)



Temperature range
 0 ... +50 °C



#### Key features

The energy efficiency module MSE6-D2M automates energy saving in compressed air systems. The intelligent module fully automatic monitors the compressed air supply. These functions are integrated into the new MSE6-D2M: automatic shut-off of the compressed air supply during breaks in production, leakage

#### **CPX** extension

Extension to the MSE6-C2M-...-M



occurring over time and reports these. It can be fully integrated into the machine network via the fieldbus node of the MSE6-C2M-...-M or CPX terminal. All measured values (pressure, flow rate, system parameters, ...) are available in the PLC/cloud and can be displayed or individually further processed.

#### - Note

The MSE6-D2M cannot be connected directly to and operated using a controller. It must be connected as an extension to the MSE6-C2M-...-M or to a CPX terminal with CPX extension.

- Energy efficiency function for two separate compressed air systems
- Leakage detection
- Connection to MSE6-C2M-...-M with CPX extension
- Only one fieldbus connection
   required
- Process monitoring
- Integrated pressure and flow rate measurement
- Fieldbus-controlled pressure regulation with automatic standby pressure reduction (MSE6-C2M only)
- Direct activation/integration of 2 digital inputs (2DI) and 2 digital outputs (2DO), e.g. for valve actuation or for the sensors (MSE6-C2M only)

Extension to the CPX terminal



Ø

- Energy efficiency function
- Leakage detection
- Connection to CPX terminal with CPX extension (note CPX system limits!)
- Cost-efficient solution with just one fieldbus node
- Process monitoring with leakage detection
- Integrated pressure and flow rate measurement
- Automatic detection of end of production and shut-off of compressed air supply

# **Energy efficiency modules MSE6-D2M, MSE series** Technical data

General technical data				
Pneumatic port 1, 2	G1/2 (connecting plate)			
Mounting position	Horizontal ±5°			
Flow direction	Unidirectional P1 $\rightarrow$ P2			
Valve function	2/2-way shut-off valve, open, monostable			
Reset method	Mechanical			

Electrical data		
Operating voltage range for	[V DC]	18 28.8
load voltage <sup>1)</sup>		
Operating voltage range for	[V DC]	18 30
electronics/sensors <sup>1)</sup>		
Current consumption for	[mA]	Max. 100 when valve is supplied with current
actuator technology		
Current consumption for	[mA]	Max. 250
electronics/sensors at 24 V		
Reverse polarity protection		For operating voltage connections
Degree of protection		IP65 with plug socket
Duty cycle	[%]	100

1) Supply via CPX extension

Standard nominal flow rate qnN <sup>1)</sup>		
Pneumatic connection	G <sup>1</sup> /2	
In main direction of flow [l/min]	4500	
$1 \rightarrow 2$		

1) Measured at p1 = 6 bar and p2 = 5 bar,  $\Delta p = 1$  bar

Operating and environmental conditions				
Operating pressure	[bar]	3.5 13		
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]		
Note on operating/		Lubricated operation not possible		
pilot medium				
Ambient temperature	[°C]	0 +50		
Temperature of medium	[°C]	0 +50		
Storage temperature	[°C]	-10 +60		
Corrosion resistance class CRC <sup>1)</sup>		2		
CE mark (see declaration of conformity)		To EU EMC Directive <sup>2)</sup>		
Certification		RCM compliance mark		

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

3) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com/sp → User documentation. If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

Display/operation		
Flow measurement		
Flow measuring range start	[l/min]	50
value		
Flow measuring range end	[l/min]	5000
value		
Accuracy of flow rate		+/- (3% of measured value + $0.3\%$ FS) <sup>1)</sup>
Displayable unit(s)		l/min (preset)
		scfm
Pressure measurement		
Pressure measuring range	[bar]	0
start value		
Pressure measuring range end	[bar]	14
value		
Accuracy in ±%FS <sup>1)</sup>	[%FS]	3
Displayable unit(s)		mbar (preset)
		kPa
		psi
Consumption measurement		
Displayable unit(s)		l (preset)
		m <sup>3</sup>
		scf

1) % FS = % of measuring range end value (full scale)

Weight		
Product weight	[g]	2700
Materials		
Housing		Die-cast aluminium
Сар		Reinforced PA
Cover		Reinforced PA
Seals		NBR

**FESTO** 

# **Energy efficiency modules MSE6-D2M, MSE series** Technical data



oracing aata					
Size	Pneumatic	Electrical actuation	Part no.	Туре	
	connection				
With CPX extension row 2					
MSE6	G1⁄2	Internal electrical actuation	8085453	MSE6-D2M-5000-CBUS-S-RG-BAR-VCB-AGD	

### Dimensions

## Service unit combinations MSE6-E2M, MSE series

Peripherals overview



# Service unit combinations MSE6-E2M, MSE series

		MSE	6	-	E2M	-	5000	-	FB34	-	AGD
	-										
Series											
MSE	Modular standard, electric		_								
Size											
6	Grid dimension 62 mm			,							
Functio	n										
E2M	Energy efficiency module										
Flow me	asuring range										
5000	5000 l/min										
Electrica	al actuation										
FB13	Fieldbus node for PROFIBUS DP									,	
FB33	Fieldbus node for PROFINET IO with M12 por	t									
FB34	Fieldbus node for PROFINET IO with RJ45 por	t									
FB35	Fieldbus node for PROFINET IO with SCRJ por	t									
FB36 Fieldbus node for Ethernet/IP											
FB37	Fieldbus node for EtherCAT										
-											
Pneuma	tic connection										
AGD	Connecting plate G <sup>1</sup> /2										

# Service unit combinations MSE6-E2M, MSE series Technical data – Fieldbus node FB13 for PROFIBUS DP

#### MSE6-E2M-...-FB13

Consisting of

- Energy efficiency module 2/2-way shut-off valve, open,
  - monostable
  - Flow sensor
  - Pressure sensor for output pressure
  - Control unit for processing measuring data, activating valves and controlling energy efficiency functions
- Fieldbus node for PROFIBUS DP









General technical data	
Pneumatic port 1, 2	G <sup>1</sup> /2 (connecting plate)
Mounting position	Horizontal ±5°
Flow direction	Unidirectional P1 $\rightarrow$ P2
Valve function	2/2-way shut-off valve, open, monostable
Reset method	Mechanical

Electrical data		
System supply		
Electrical connection		Plug M18x1, 4-pin
Operating voltage range for	[V DC]	18 26.4
load voltage		
Operating voltage range for	[V DC]	18 30
electronics/sensors		
Current consumption for	[mA]	Max. 100 when valve is supplied with current
actuator technology		
Current consumption for [mA] A		Max. 300
electronics/sensors at 24 V	electronics/sensors at 24 V	
Reverse polarity protection		For operating voltage connections
Degree of protection		IP65 with plug socket
Duty cycle	[%]	100
Fieldbus connection		
Fieldbus interface		Sub-D socket, 9-pin

Standard nominal flow rate qnN <sup>1)</sup>		
Pneumatic connection	G1⁄2	
In main direction of flow [l/min]	4500	
$1 \rightarrow 2$		

1) Measured at p1 = 6 bar and p2 = 5 bar,  $\Delta p = 1$  bar

# Service unit combinations MSE6-E2M, MSE series Technical data – Fieldbus node FB13 for PROFIBUS DP

Operating and environmenta	l conditions	
Operating pressure	[bar]	4 10
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Note on operating/		Lubricated operation not possible
pilot medium		
Ambient temperature	[°C]	0 +50
Temperature of medium	[°C]	0 +50
Storage temperature	[°C]	-10 +60
Corrosion resistance class CR	C <sup>1)</sup>	2
CE mark (see declaration of conformity)		To EU EMC Directive <sup>2)</sup>
Certification		RCM compliance mark

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmo-sphere typical for industrial applications.

2) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com/sp → User documentation.

If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

#### Display/operation

Flow measurement		
Flow measuring range start	[l/min]	50
value		
Flow measuring range end	[l/min]	5000
value		
Accuracy of flow rate		+/- (3% of measured value + 0.3% FS) <sup>1)</sup>
Displayable unit(s)		l/min (preset)
		scfm
Pressure measurement		
Pressure measuring range	[bar]	0
start value		
Pressure measuring range end	[bar]	14
value		
Accuracy in ±%FS <sup>1)</sup>	[%FS]	3
Displayable unit(s)		mbar (preset)
		kPa
		psi
Consumption measurement		
Displayable unit(s)		l (preset)
		m <sup>3</sup>
		scf

1) % FS = % of measuring range end value (full scale)

Weight							
Product weight	[g]	3300					

Materials				
Housing	Die-cast aluminium			
Сар	Reinforced PA			
Cover	Reinforced PA			
Seals	NBR			

# Service unit combinations MSE6-E2M, MSE series Technical data – Fieldbus node FB13 for PROFIBUS DP

Pin allocation, system supply		
Plug M18x1, 4-pin	Pin	Meaning
	1	Operating voltage for electronics/sensors +24 V DC
1 - (+ + +) - 2	2	Operating voltage for actuator technology +24 V DC
4 + + - 3	3	0 V
	4	Functional earth



Ordering data				
Size	Pneumatic	Electrical actuation	Part no.	Туре
	connection			
MSE6	G1⁄2	Fieldbus node FB13 for PROFIBUS DP	2465321	MSE6-E2M-5000-FB13-AGD

# **Service unit combinations MSE6-E2M, MSE series** Technical data – Fieldbus node FB33/FB34/FB35 for PROFINET IO

- 📥 -

-

#### MSE6-E2M-...-FB33/FB34/FB35

Consisting of

- Energy efficiency module - 2/2-way shut-off valve, open,
  - monostable

  - Pressure sensor for output pressure
  - Control unit for processing measuring data, activating valves and controlling energy efficiency functions
- Fieldbus node for PROFINET IO



4 ... 10 bar

Operating pressure



General technical data	
Pneumatic port 1, 2	G <sup>1</sup> / <sub>2</sub> (connecting plate)
Mounting position	Horizontal ±5°
Flow direction	Unidirectional P1 $\rightarrow$ P2
Valve function	2/2-way shut-off valve, open, monostable
Reset method	Mechanical

Electrical data					
Туре		MSE6-E2MFB33	MSE6-E2MFB34	MSE6-E2MFB35	
System supply					
Electrical connection		Plug M18x1, 4-pin			
Operating voltage range for	[V DC]	18 26.4			
load voltage					
Operating voltage range for	[V DC]	18 30			
electronics/sensors					
Current consumption for	[mA]	Max. 100 when valve is supplied with current			
actuator technology					
Current consumption for	[mA]	Max. 320	Max. 320	Max. 400	
electronics/sensors at 24 V					
Reverse polarity protection		For operating voltage connections			
Degree of protection		IP65 with plug socket			
Duty cycle	[%]	100			
Fieldbus connection					
Fieldbus interface		2x M12x1 socket, 4-pin, D-coded	2x RJ45 push-pull socket, AIDA	2x SCRJ push-pull socket, AIDA	

Standard nominal flow rate qnN <sup>1)</sup>			
Pneumatic connection	G <sup>1</sup> /2		
In main direction of flow [l/min]	4500		
$1 \rightarrow 2$			

1) Measured at p1 = 6 bar and p2 = 5 bar,  $\Delta p = 1$  bar

# - Flow sensor

# **Service unit combinations MSE6-E2M, MSE series** Technical data – Fieldbus node FB33/FB34/FB35 for PROFINET IO

Operating and environmental conditions			
Operating pressure	[bar]	410	
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on operating/		Lubricated operation not possible	
pilot medium			
Ambient temperature	[°C]	0+50	
Temperature of medium	[°C]	0 +50	
Storage temperature	[°C]	-10 +60	
Corrosion resistance class CRC	_1)	2	
CE mark (see declaration of conformity)		To EU EMC Directive <sup>2)</sup>	
Certification		RCM compliance mark	

1) Corrosion resistance class CRC 2 to Festo standard FN 940070 Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com/sp > User documentation. 2)

If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

Display/operation		
Flow measurement		
Flow measuring range start	[l/min]	50
value		
Flow measuring range end	[l/min]	5000
value		
Accuracy of flow rate		+/- (3% of measured value + 0.3% FS) <sup>1)</sup>
Displayable unit(s)		l/min (preset)
		scfm
Pressure measurement		
Pressure measuring range	[bar]	0
start value		
Pressure measuring range end	[bar]	14
value		
Accuracy in ±%FS <sup>1)</sup>	[%FS]	3
Displayable unit(s)		mbar (preset)
		kPa
		psi
Consumption measurement		
Displayable unit(s)		l (preset)
		m <sup>3</sup>
		scf

1) % FS = % of measuring range end value (full scale)

Weight				
Туре		MSE6-E2MFB33	MSE6-E2MFB34	MSE6-E2MFB35
Product weight	[g]	3350	3450	3450

Materials

Materials	
Housing	Die-cast aluminium
Сар	Reinforced PA
Cover	Reinforced PA
Seals	NBR

## Service unit combinations MSE6-E2M, MSE series

Technical data – Fieldbus node FB33/FB34/FB35 for PROFINET IO

Pin allocation, system supply		
Plug M18x1, 4-pin	Pin	Meaning
	1	Operating voltage for electronics/sensors +24 V DC
1 - (+ +) - 2	2	Operating voltage for actuator technology +24 V DC
4-++-3	3	0 V
	4	Functional earth

#### Dimensions

Fieldbus node FB33 for PROFINET IO with M12 port



**FESTO** 

Download CAD data → www.festo.com

# **Service unit combinations MSE6-E2M, MSE series** Technical data – Fieldbus node FB33/FB34/FB35 for PROFINET IO

### **FESTO**

Download CAD data → www.festo.com

#### Dimensions



Туре	D1	L1	L2	L3	L4	L5	L6	L7	L8	L9
MSE6-E2MFB34/FB35	G1⁄2	285	98	217	197	86	7	21	292	147

Ordering data				
Size	Pneumatic	Electrical actuation	Part no.	Туре
	connection			
MSE6	G1⁄2	Fieldbus node FB33 for PROFINET IO with M12 port	3850287	MSE6-E2M-5000-FB33-AGD
		Fieldbus node FB34 for PROFINET IO with RJ45 port	3869585	MSE6-E2M-5000-FB34-AGD
		Fieldbus node FB35 for PROFINET IO with SCRJ port	3870296	MSE6-E2M-5000-FB35-AGD

Subject to change - 2019/05

## Service unit combinations MSE6-E2M, MSE series

- **\_** -

-

Technical data – Fieldbus node FB36 for Ethernet/IP and FB37 for EtherCAT

#### MSE6-E2M-...-FB36/FB37

Consisting of

- Energy efficiency module
   2/2-way shut-off valve, open,
  - monostable
  - Flow sensor
  - Pressure sensor for output pressure
  - Control unit for processing measuring data, activating valves and controlling energy efficiency functions
- Fieldbus node for Ethernet/IP or EtherCAT

### General technical data



Operating pressure

Temperature range

4 ... 10 bar



General technical data	
Pneumatic port 1, 2	G <sup>1</sup> /2 (connecting plate)
Mounting position	Horizontal ±5°
Flow direction	Unidirectional P1 $\rightarrow$ P2
Valve function	2/2-way shut-off valve, open, monostable
Reset method	Mechanical

Electrical data		
System supply		
Electrical connection		Plug M18x1, 4-pin
Operating voltage range for	[V DC]	18 26.4
load voltage		
Operating voltage range for	[V DC]	18 30
electronics/sensors		
Current consumption for	[mA]	Max. 100 when valve is supplied with current
actuator technology		
Current consumption for	[mA]	Max. 300
electronics/sensors at 24 V		
Reverse polarity protection		For operating voltage connections
Degree of protection		IP65 with plug socket
Duty cycle	[%]	100
Fieldbus connection		
Fieldbus interface		2x M12x1 socket, 4-pin, D-coded

Standard nominal flow rate qnN <sup>1)</sup>					
Pneumatic connection	G <sup>1</sup> /2				
In main direction of flow [l/min]	4500				
$1 \rightarrow 2$					

1) Measured at p1 = 6 bar and p2 = 5 bar,  $\Delta p = 1$  bar



# **Service unit combinations MSE6-E2M, MSE series** Technical data – Fieldbus node FB36 for Ethernet/IP and FB37 for EtherCAT

Operating and environmental conditions						
Operating pressure [bar]	]	4 10				
Operating medium	1	Compressed air to ISO 8573-1:2010 [7:4:4]				
Note on operating/		Lubricated operation not possible				
pilot medium						
Ambient temperature [°C]		0 +50				
Temperature of medium [°C]		0 +50				
Storage temperature [°C]		-10 +60				
Corrosion resistance class CRC <sup>1)</sup>		2				
CE mark (see declaration of conformity)		To EU EMC Directive <sup>2)</sup>				
Certification		RCM compliance mark				

Corrosion resistance class CRC 2 to Festo standard FN 940070 Moderate corrosion stress. Indoor applications in which condensation may occur. External visible parts with primarily decorative requirements for the surface and which are in direct contact with the ambient atmosphere typical for industrial applications.

For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com/sp > User documentation. 2)

If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

Display/operation		
Flow measurement		
Flow measuring range start	[l/min]	50
value		
Flow measuring range end	[l/min]	5000
value		
Accuracy of flow rate		+/- (3% of measured value + 0.3% FS) <sup>1)</sup>
Displayable unit(s)		l/min (preset)
		scfm
Pressure measurement		
Pressure measuring range	[bar]	0
start value		
Pressure measuring range end	[bar]	14
value		
Accuracy in ±%FS <sup>1)</sup>	[%FS]	3
Displayable unit(s)		mbar (preset)
		kPa
		psi
Consumption measurement		
Displayable unit(s)		l (preset)
		m <sup>3</sup>
		scf

1) % FS = % of measuring range end value (full scale)

Weight						
Product weight	[g]	3300				
Matailala						

Materials	
Housing	Die-cast aluminium
Сар	Reinforced PA
Cover	Reinforced PA
Seals	NBR

# **Service unit combinations MSE6-E2M, MSE series** Technical data – Fieldbus node FB36 for Ethernet/IP and FB37 for EtherCAT

Pin allocation, system supply					
Plug M18x1, 4-pin	Pin	Meaning			
	1	Operating voltage for electronics/sensors +24 V DC			
$1 - \left( + + + \right) - 2$	2	Operating voltage for actuator technology +24 V DC			
4-++-3	3	0 V			
	4	Functional earth			



Ordering data						
Size	Pneumatic	Electric actuation	Part no.	Туре		
	connection					
MSE6	G1⁄2	Fieldbus node FB36 for EtherNet/IP	3990296	MSE6-E2M-5000-FB36-AGD		
		Fieldbus node FB37 for EtherCAT	3992150	MSE6-E2M-5000-FB37-AGD		

### **FESTO**

Technical data → Internet: ntsd

Ordering data – P	ower supply socket NECU-M-P		Technical data 🗲 Internet: necu	
Description		Electrical connection	Part no.	Туре
	For MSE6-C2M	5-pin, push-pull, connection pattern PP, fulfils requirements to AIDA	5195383	NECU-M-PPG5PP-C1-PN

### Ordering data – Plug socket NTSD

Description Electrical connection		Electrical connection	l		Туре
OT T	For MSE6-E2M	Straight socket, 4-pin	Screw terminal Pg9, connection cross section 1.5 mm <sup>2</sup>	18493	NTSD-GD-9
			Screw terminal Pg13, connection cross section 2.5 mm <sup>2</sup>	18526	NTSD-GD-13,5
	For MSE6-E2M	Angled socket, 4-pin	Screw terminal Pg9, connection cross section 1.5 mm <sup>2</sup>	18527	NTSD-WD-9

Ordering data – Pl	lug FBS-SUB-9			Technical data → Internet: fbs-sub-9
Description		Electrical connection	Part no.	Туре
	For fieldbus node FB13 for PROFIBUS DP	Plug, 9-pin, Sub-D	532216	FBS-SUB-9-GS-DP-B

Ordering data –	Plug NECU-M-S-D12G4				Technical data 🗲 Internet: necu
Description		Electrical connection		Part no.	Туре
	For fieldbus node FB33 for PROFINET IO, for fieldbus node FB36 for EtherNet/IP, for fieldbus node FB37 for EtherCAT	Plug M12x1, 4-pin, D-coded	Screw terminal, can be screened	543109	NECU-M-S-D12G4-C2-ET

Ordering data – P	lug FBS-RJ45			Technical data 🗲 Internet: fbs
Description		Electrical connection	Part no.	Туре
	For fieldbus node FB34 for PROFINET IO	Plug RJ45, 8-pin, push-pull	552000	FBS-RJ45-PP-GS

Ordering data – P	lug FBS-SCRJ			Technical data 🗲 Internet: fbs
Description		Electrical connection	Part no.	Туре
	For fieldbus node FB35 for PROFINET IO	Plug SCRJ, 2-pin, push-pull	571017	FBS-SCRJ-PP-GS

Ordering data – O	Technical data 🗲 Internet: nebc				
Description Electrical connection		Part no.	Туре		
For MSE6-C2M/D2M	For MSE6-C2M/D2M	8-pin	0.25 m	564189	NEBC-F12G8-KH-0.25-N-S-F12G8
			0.5 m	564190	NEBC-F12G8-KH-0.5-N-S-F12G8
			1 m	564191	NEBC-F12G8-KH-1-N-S-F12G8
			1.5 m	564192	NEBC-F12G8-KH-1.5-N-S-F12G8
			2 m	576015	NEBC-F12G8-KH-2-N-S-F12G8

Ordering data – Connecting cable NEBU-M12					Technical data 🗲 Internet: nebu	
Description		Electrical connection			Part no.	Туре
	For MSE6-C2M	Straight socket, 5-pin	Open cable end,	2.5 m	541330	NEBU-M12G5-K-2.5-LE5
TO THE NUMBER OF THE OWNER OWNER OF THE OWNER OWNER OF THE OWNER OWNE OWNER			5-wire	5 m	541331	NEBU-M12G5-K-5-LE5
		Angled socket, 5-pin	Open cable end,	2.5 m	567843	NEBU-M12W5-K-2.5-LE5
			5-wire	5 m	567844	NEBU-M12W5-K-5-LE5
	For MSE6-C2M	Straight socket, 5-pin	Angled plug, 5-pin	0.5 m	8003617	NEBU-M12G5-K-0.5-M12W5
Car Stand				2 m	8003618	NEBU-M12G5-K-2-M12W5
Ser and the series of the seri		Angled socket, 5-pin	Angled plug, 5-pin	0.5 m	570733	NEBU-M12W5-K-0.5-M12W5
				2 m	570734	NEBU-M12W5-K-2-M12W5

Ordering data	- Wall mounting SET MS6-WPG			Technical data 🗲 Internet: ms6-wpg
Description			Part no.	Туре
	For MSE6-C2M/D2M/E2M	<ul> <li>For connecting modules for wall mounting</li> <li>Same wall gap for combining series MS6 and MSE6</li> </ul>	8072794	MS6-WPG

Ordering data – Module connector MS6-MV-EX				Technical data 🗲 Internet: ms6-mv
Description			Part no.	Туре
	For MSE6-C2M/D2M/E2M	For connecting modules	541543	MS6-MV-EX

Ordering data – Silencers U				Technical data 🗲 Internet: u
Description			Part no.	Туре
	For MSE6-C2M	• For noise reduction	6842	U-1/4-B

## **Festo - Your Partner in Automation**





1 Festo Inc.

5300 Explorer Drive Mississauga, ON L4W 5G4 Canada

Festo Customer Interaction Center Tel: 18774633786 Fax: 18773933786 Email: customer.service.ca@festo.com ventas.mexico@festo.com



2 Festo Pneumatic

Av. Ceylán 3, Col. Tequesquináhuac 54020 Tlalnepantla, Estado de México

**Multinational Contact Center** 01 800 337 8669



3 Festo Corporation 1377 Motor Parkway Suite 310 Islandia, NY 11749



4 **Regional Service Center** 7777 Columbia Road Mason, OH 45040

**Festo Customer Interaction Center** 1 800 993 3786 1 800 963 3786 customer.service.us@festo.com

Subject to change

f 🗾 in 🛗 www.festo.com/socialmedia

Connect with us



www.festo.com