



- Resistant to corrosion caused by harsh ambient conditions
- Easy to clean design
- Wide choice of variants
- Comprehensive range of accessories

Specified types in accordance with ATEX directive for potentially explosive atmospheres
➔ www.festo.com/en/ex

Corrosion-resistant cylinders

Features

FESTO

Cylinder applications

Reliable components need to achieve 100% operational reliability, even in harsh operating conditions. The aim is to maximise availability of machinery while minimising downtimes. Corrosion-resistant cylinders are therefore used in applications where the surface finish of normal pneumatic drives would render them non-resistant to the surrounding media. However designing a corrosion-resistant system involves more than simply selecting a suitable steel – it also requires the selection of a tailored concept for mounting components and accessories.

Cylinder strengths

Festo's corrosion-resistant cylinders are made from highly resistant materials such as 1.4301 and 1.4401. These popular high-alloy, stainless austenitic chrome/nickel and chrome/nickel/molybdenum steels protect against chemical or electrochemical stress as well as damage to the material surface caused by cleaning or detergents. The indicated groups of materials are particularly resistant to uniform surface corrosion and offer increased protection against pitting and crevice corrosion.

Cylinder advantages

Festo's worldwide service network ensures optimum availability of corrosion-resistant cylinders. As well as a comprehensive range of standard cylinders to DIN ISO 6431 and 6432, we also offer a range of tailored mounting components and accessories. The corrosion-resistant cylinders are assembled with USDA-H1 lubricating grease and wiper seals in accordance with BGV (Federal Institute for Risk Assessment) guidelines. This means that they are suitable for use in the food industry and for direct contact with food products. We will be pleased to answer any inquiries you may have about future additions to our corrosion-resistant range. Just give us a call.

Good to know

Our many years of experience in the area of stainless steel can be invaluable when you are investigating solutions for aggressive environment. Our experts can answer any questions you might have about surface finishes and chemical resistance.



The atmosphere in the curing cellar of a cheese factory consists of an unpleasant mix of ammonia, lactic acid and 98% humidity.



An area subject to radiation of up to 4 sievert/h whilst immersed in fully desalinated water in a manipulator for dismantling nuclear reactor pressure reservoirs and thermal shields.

Corrosion-resistant cylinders

Features

Resistance

Complete resistance to pitting and crevice corrosion is not always possible, even with ideal application parameters. The following parameters increase the pitting effect of chloride ions:

- Concentration of chloride ions
- Duration of contact
- Temperature
- Increasing pH value

It must therefore be ensured during design, assembly and operation that all parts of the machinery can be properly cleaned to avoid an accumulation of chloride ions.

Selected sealing materials ensure very high resistance to a wide range of chemical compounds.

Further information on resistance to media can be obtained on the Internet at www.festo.com.

In principle, we recommend that the cylinder be cleaned with the piston rod in the retracted position to avoid the risk of washing out the lifetime lubrication.

Various types of machinery contamination make cleaning processes necessary in many industrial sectors.

The degree of cleaning required ranges from wiping the machinery to wet cleaning to foam cleaning with different exposure times and concentrations.

It is therefore impossible to make a general recommendation on compatibility.



Wet cleaning











Foam cleaning

Corrosion-resistant cylinders

Product range overview

FESTO

Function	Design	Type	Conforms to	Piston Ø	Stroke
Double-acting	Round cylinders				
		CRDG Piston rod at one end	–	12, 16	1 ... 200
				20	1 ... 320
				25, 32, 40, 50, 63	1 ... 500
		CRDSW Piston rod at one end	–	32, 40, 50, 63	1 ... 500
		CRHD ... MQ Bearing cap with male thread	–	32, 40, 50, 63, 80, 100	10 ... 500 Special lengths on request
		CRHD ... MC End cap with yoke	–	32, 40, 50, 63, 80, 100	10 ... 500 Special lengths on request
		CRHD ... MS End cap with lug	–	32, 40, 50, 63, 80, 100	10 ... 500 Special lengths on request
	Standard cylinders				
		CRDSNU Piston rod at one end	ISO 6432	12, 16	10 ... 200
				20	10 ... 320
				25	10 ... 500
		CRDSNU- ... -S2 Through piston rod		12, 16	10 ... 200
				20	10 ... 320
				25	10 ... 500
		CRDNG Piston rod at one end	ISO 15552 (ISO 6431 and VDMA 24562)	32, 40, 50, 63, 80, 100, 125	10 ... 2000
				32, 40, 50, 63, 80, 100, 125	10 ... 2000
		CRDNG- ... -S2 Through piston rod			
	Standard cylinders with swivel bearing at rear				
		CRDNGS Piston rod at one end	ISO 15552 (ISO 6431 and VDMA 24562)	32, 40, 50, 63, 80, 100, 125	10 ... 2000

Corrosion-resistant cylinders

Product range overview

FESTO

Type	Position sensing	Cushioning		Heat resistant	→ Page
		Non-adjustable at both ends	Adjustable at both ends		
		P	PPV		
	A			S6	
Round cylinders					
CRDG Piston rod at one end	■	■	–	–	1 / 2.7-6
CRDSW Piston rod at one end	■	■	–	–	1 / 2.7-12
CRHD ... MQ Bearing cap with male thread	■	–	■	■	1 / 2.7-17
CRHD ... MC End cap with yoke	■	–	■	■	1 / 2.7-17
CRHD ... MS End cap with lug	■	–	■	■	1 / 2.7-17
Standard cylinders					
CRDSNU Piston rod at one end	■	■	–	–	1 / 2.7-24
CRDSNU- ... -S2 Through piston rod	■	■	–	–	1 / 2.7-24
CRDNG Piston rod at one end	■	–	■	■	1 / 2.7-30
CRDNG- ... -S2 Through piston rod	■	–	■	■	1 / 2.7-30
Standard cylinders with swivel bearing at rear					
CRDNGS Piston rod at one end	■	–	■	■	1 / 2.7-30

Cylinders with piston rods
Corrosion-resistant cylinders

2.7


Round cylinders CRDG, corrosion-resistant

Peripherals overview


FESTO

CRDG

Piston $\varnothing$ 12 ... 25 mm



Piston $\varnothing$ 32 ... 63 mm




Mounting options

Piston $\varnothing$ 12 ... 25 mm

Threaded mounting


Mounting with hex nut



Piston $\varnothing$ 32 ... 63 mm

Threaded mounting

Mounting with slotted nut



Round cylinders CRDG, corrosion-resistant

Peripherals overview

FESTO

Mounting attachments and accessories				
	Brief description	Piston Ø 12 ... 25 mm	Piston Ø 32 ... 63 mm	→ Page
1	Rod eye CRSGS	■	■	1 / 2.8-9
2	Rod clevis CRSG	■	■	1 / 2.8-9
3	Flange mounting CRFBN	■	–	1 / 2.8-3
4	Foot mounting CRHBN	■	–	1 / 2.8-1
5	Flange mounting CRFV	–	■	1 / 2.8-3
6	Clevis foot CRSBS	–	■	1 / 2.8-7
7	Pivot bolt CRGBS	–	■	1 / 2.8-7
8	Proximity sensor CRSMEO-4	■	■	1 / 2.8-9
9	Mounting kit CRSMBR	■	■	1 / 2.8-9
10	One-way flow control valve CRGRLA	■	■	1 / 2.8-9
11	Push-in/threaded fitting CRQS	■	■	Volume 3

Round cylinders CRDG, corrosion-resistant

Type code

FESTO

CRDG – 50 – 80 – P – A

Type

Double-acting

CRDG Round cylinder

Piston Ø [mm]

Stroke [mm]

Cushioning

P Non-adjustable at both ends

Sensing


A Position sensing

Round cylinders CRDG, corrosion-resistant

Technical data

FESTO

Function



[www.festo.com/en/
Spare_parts_service](http://www.festo.com/en/Spare_parts_service)



-  Diameter
12 ... 63 mm
-  Stroke length
1 ... 500 mm

General technical data								
Piston Ø	12	16	20	25	32	40	50	63
Pneumatic connection	M5	M5	G $\frac{1}{8}$	G $\frac{1}{8}$	G $\frac{1}{8}$	G $\frac{1}{4}$	G $\frac{1}{4}$	G $\frac{3}{8}$
Piston rod thread	M6	M6	M8	M10x1.25	M10x1.25	M12x1.25	M16x1.5	M16x1.5
Constructional design	Piston							
	Piston rod							
	Cylinder barrel							
Cushioning	Non-adjustable at both ends							
Position sensing	For proximity sensing							
Type of mounting	With accessories							
	With male thread							
Mounting position	Any							

Operating and environmental conditions								
Piston Ø	12	16	20	25	32	40	50	63
Operating medium	Filtered compressed air, lubricated or unlubricated							
Operating pressure	1 ... 10 bar							
Ambient temperature ¹⁾ [°C]	-20 ... +80							
Corrosion resistance class CRC ²⁾	4							

1) Note operating range of proximity sensors

2) Corrosion resistance class 4 according to Festo standard 940 070

Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required

Forces [N]								
Piston Ø	12	16	20	25	32	40	50	63
Theoretical force at 6 bar, advancing	68	121	189	295	483	754	1 178	1 870
Theoretical force at 6 bar, retracting	51	104	158	247	415	633	990	1 682

Weights [g]								
Piston Ø	12	16	20	25	32	40	50	63
Basic weight at 0 mm stroke	80	120	270	360	560	1 160	1 950	2 964
Additional weight per 10 mm stroke	4	6	8	12	18	22	35	41

Cylinders with piston rods
Corrosion-resistant cylinders

2.7


Round cylinders CRDG, corrosion-resistant

Technical data

FESTO

Materials

Sectional view




Cylinder

1	Piston rod	High-alloy stainless steel
2	Bearing cap	High-alloy stainless steel
3	Cylinder barrel	High-alloy stainless steel
4	End cap	High-alloy stainless steel
–	Seals	Polyurethane

Dimensions

Download CAD data → www.festo.com/en/engineering

Piston Ø 12 ... 25mm



Ø [mm]	AM	B Ø h9	BE	BF	D Ø	D4 Ø	EE	EW	KK	KV	KW	MM Ø f8	L2	PL	VD	WF	ZJ	≈G1
12	16	16	M16x1.5	16	20	13.3	M5	11	M6	24	8	6	44	6	2	22	66	5
16	16	16	M16x1.5	16	20	17.3	M5	15	M6	24	8	6	51	6	2	22	73	5
20	20	22	M22x1.5	19	30	21.3	G½	18	M8	32	11	8	60	8.2	2	24	84	7
25	22	22	M22x1.5	21	30	26.5	G½	21	M10x1.25	32	11	10	61	8.2	2	28	89	9

Round cylinders CRDG, corrosion-resistant


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com/en/engineering

Piston Ø 32 ... 63 mm



Ø	AM	B Ø h9	B1	B2	BE	BF	BG	D Ø	D1 Ø	D4 Ø	EE
[mm]											
32	20	30	38	36.8	M30x1.5	30	6.6	40	42	33.6	G1/8
40	24	38	46	44.8	M38x1.5	35	9.6	49	50	41.6	G1/4
50	32	45	57	55.8	M45x1.5	38	12.6	59	60	52.4	G1/4
63	32	45	70	67	M45x1.5	38	15.5	70	60	65.4	G3/8

Ø	KK	KW	MM Ø	L2	RT	PL	VD	WF	ZJ	⌀1	⌀2
[mm]											
32	M10x1.25	8	12	85.7	M8x1	9	2	38.2	123.9	10	27
40	M12x1.25	10	16	100	M10x1	12	3	45.2	145.2	13	36
50	M16x1.5	10	20	107.6	M12x1.5	12	3	50.2	157.8	17	46
63	M16x1.5	10	20	107.8	M14x1.5	13	3	50.2	168	17	55

Ordering data

	Piston Ø [mm]	Stroke [mm]	Part No.	Type
	12	1 ... 200	160 980	CRDG-12-...-P-A
	16		160 981	CRDG-16-...-P-A
	20	1 ... 320	160 982	CRDG-20-...-P-A
	25	1 ... 500	160 983	CRDG-25-...-P-A
	32		160 984	CRDG-32-...-P-A
	40		160 985	CRDG-40-...-P-A
	50		160 986	CRDG-50-...-P-A
	63		160 987	CRDG-63-...-P-A


Cylinders with piston rods
Corrosion-resistant cylinders

2.7

Round cylinders CRDSW, corrosion-resistant

Peripherals overview



FESTO



Mounting options

Threaded mounting

Mounting with slotted nut



Mounting attachments and accessories

	Brief description	→ Page
1 Rod eye CRSGS	With spherical bearing	1 / 2.8-9
2 Rod clevis CRSG	Permits a swivelling movement of the cylinder in one plane	1 / 2.8-9
3 Foot mounting CRH (2 pieces)	For bearing and end cap	1 / 2.8-1
3 Flange mounting CRFV	For bearing and end cap	1 / 2.8-3
4 Clevis foot CRSBS	For bearing and end cap	1 / 2.8-7
5 Pivot bolt CRGBS	For bearing and end cap	1 / 2.8-7
6 Proximity sensor CRSME0-4	With LED for operating status indication	1 / 2.8-9
7 Mounting kit CRSMBR	For proximity sensor CRSME0-4	1 / 2.8-9
8 One-way flow control valve CRGRLA	For speed regulation	1 / 2.8-9
9 Push-in/threaded fitting CRQS	For connecting compressed air tubing with standard O.D.	Volume 3

Round cylinders CRDSW, corrosion-resistant



Type code


		CRDSW	-	50	-	80	-	P	-	A
Type										
Double-acting										
CRDSW	Round cylinder									
Piston $\varnothing$ [mm]										
Stroke [mm]										
Cushioning										
P	Non-adjustable at both ends									
Sensing										
A	Position sensing									

Round cylinders CRDSW, corrosion-resistant

Technical data

FESTO

Function



[www.festo.com/en/
Spare_parts_service](http://www.festo.com/en/Spare_parts_service)



-  - Diameter
32 ... 63 mm
-  - Stroke length
1 ... 500 mm

General technical data				
Piston Ø	32	40	50	63
Pneumatic connection	G $\frac{1}{8}$	G $\frac{1}{4}$	G $\frac{1}{4}$	G $\frac{3}{8}$
Piston rod thread	M10x1.25	M12x1.25	M16x1.5	M16x1.5
Constructional design	Piston			
	Piston rod			
	Cylinder barrel			
Cushioning	Non-adjustable at both ends			
Position sensing	For proximity sensing			
Type of mounting	With accessories			
	With male thread			
Mounting position	Any			

Operating and environmental conditions				
Piston Ø	32	40	50	63
Operating medium	Filtered compressed air, lubricated or unlubricated			
Operating pressure	1 ... 10 bar			
Ambient temperature ¹⁾ [°C]	-20 ... +80			
Corrosion resistance class CRC ²⁾	4			

1) Note operating range of proximity sensors

2) Corrosion resistance class 4 according to Festo standard 940 070

Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required

Forces [N]				
Piston Ø	32	40	50	63
Theoretical force at 6 bar, advancing	483	754	1 178	1 870
Theoretical force at 6 bar, retracting	415	633	990	1 682

Weights [g]				
Piston Ø	32	40	50	63
Basic weight at 0 mm stroke	670	1 460	1 960	3 325
Additional weight per 10 mm stroke	18	22	35	41



Pneumatic sizing using Pro Pneu
www.festo.com/en/engineering


Round cylinders CRDSW, corrosion-resistant

Technical data



Materials

Sectional view



Cylinder		
1	Piston rod	High-alloy stainless steel
2	Bearing cap	High-alloy stainless steel
3	Cylinder barrel	High-alloy stainless steel
4	End cap	High-alloy stainless steel
–	Seals	Polyurethane


Round cylinders CRDSW, corrosion-resistant

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com/en/engineering



Ø	AM	B	B1	B2	BE	BF	BG	D	D1	D4	EE
[mm]		Ø h9						Ø	Ø	Ø	
32	20	30	38	36.8	M30x1.5	30	6.6	40	42	33.6	G1/8
40	24	38	46	44.8	M38x1.5	35	9.6	49	50	41.6	G1/4
50	32	45	57	55.8	M45x1.5	38	12.6	59	60	52.4	G1/4
63	32	45	70	67	M45x1.5	38	15.5	70	60	65.4	G3/8

Ø	KK	KW	MM	L2	RT	PL	VA	VD	WF	ZJ	⌀1
[mm]			Ø								
32	M10x1.25	8	12	96	M8x1	9	14	2	38.2	134	10
40	M12x1.25	10	16	113	M10x1	12	16	3	45.2	158	13
50	M16x1.5	10	20	120	M12x1.5	12	18	3	50.2	170	17
63	M16x1.5	10	20	124	M14x1.5	13	18	3	50.2	174	17


Ordering data

	Piston Ø [mm]	Stroke [mm]	Part No.	Type
	32	1 ... 500	160 676	CRDSW-32-...-P-A
	40		160 677	CRDSW-40-...-P-A
	50		160 678	CRDSW-50-...-P-A
	63		160 679	CRDSW-63-...-P-A

Round cylinders CRHD, corrosion-resistant

Peripherals overview

FESTO



Mounting attachments and accessories						
	Brief description	CRHD-MQ	CRHD-MC	CRHD-MS	➔ Page	
1	Rod eye CRSGS	With spherical bearing	■	■	■	1 / 2.8-9
2	Rod clevis CRSG	Permits a swivelling movement of the cylinder in one plane	■	■	■	1 / 2.8-9
3	Ring nut CR	For bearing cap	■	–	–	1 / 2.8-8
4	Clevis foot CRLMC	For end cap	–	■	–	1 / 2.8-8
5	Proximity sensor CRSMT	With LED for operating status indication	■	■	■	1 / 2.8-9
6	Mounting kit CRSMB-8-32/100	For proximity sensor CRSMT	■	■	■	1 / 2.8-9
7	One-way flow control valve CRGRLA	For speed regulation	■	■	■	1 / 2.8-9
8	Push-in/threaded fittings CRQS	For connecting compressed air tubing with standard O.D.	■	■	■	Volume 3

Round cylinders CRHD, corrosion-resistant

Type code

FESTO

CRHD – 50 – 80 – PPV – A – MQ – S6

Type

Double-acting

CRHD Round cylinder

Piston $\varnothing$ [mm]

Stroke [mm]

Cushioning

PPV Adjustable at both ends

Sensing

A Position sensing

Cover variant

MQ Bearing cap with male thread

MC End cap with yoke

MS End cap with lug

Variant


S6 Heat resistant up to 120 °C

Round cylinders CRHD, corrosion-resistant

Technical data

FESTO

Function



-  Diameter
32 ... 100 mm
-  Stroke length
10 ... 500 mm
-  www.festo.com/en/Spare_parts_service

Variants



S6

The variant S6 is not suitable for direct contact with food products because of the seals and the grease used.



General technical data						
Piston Ø	32	40	50	63	80	100
Pneumatic connection	G $\frac{1}{8}$	G $\frac{1}{8}$	G $\frac{1}{4}$	G $\frac{3}{8}$	G $\frac{3}{8}$	G $\frac{3}{8}$
Piston rod thread	M10x1.25	M12x1.25	M16x1.5	M16x1.5	M20x1.5	M20x1.5
Constructional design	Piston					
	Piston rod					
	Cylinder barrel					
Cushioning	Adjustable at both ends					
Cushioning length	17	19.5	21	21	31	31
Position sensing	For proximity sensing					
Type of mounting	With accessories					
Mounting position	Any					

Operating and environmental conditions		
Variant	CRHD	S6
Operating medium	Filtered compressed air, lubricated or unlubricated	
Operating pressure	1 ... 10 bar	
Ambient temperature ¹⁾ [°C]	-20 ... +80	0 ... +120
Corrosion resistance class CRC ²⁾	4	

1) Note operating range of proximity sensors

2) Corrosion resistance class 4 according to Festo standard 940 070

Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required

Forces [N]						
Piston Ø	32	40	50	63	80	100
Theoretical force at 6 bar, advancing	483	754	1 178	1 870	3 016	4 712
Theoretical force at 6 bar, retracting	415	633	990	1 682	2 721	4 418

Weights [g]						
Piston Ø	32	40	50	63	80	100
Basic weight at 10 mm stroke	676	1 196	1 849	2 977	5 172	8 472
Additional weight per 10 mm stroke	26	42	57	65	100	115
Moving load at 10 mm stroke	106	198	340	398	717	968
Additional load per 10 mm stroke	9	16	25	25	38	38


Round cylinders CRHD, corrosion-resistant

Technical data


FESTO

Permissible lateral force F_q as a function of stroke length l

Horizontal mounting




Vertical mounting



- 1 Ø 32
- 2 Ø 40
- 3 Ø 50, 63
- 4 Ø 80, 100

Materials

Sectional view



Cylinder	CRHD	S6
1 Piston rod	High-alloy stainless steel	
2 Bearing cap	High-alloy stainless steel	
3 Cylinder barrel	High-alloy stainless steel	
4 End cap	High-alloy stainless steel	
- Seals	Polyurethane, nitrile rubber	Fluorocarbon rubber

Round cylinders CRHD, corrosion-resistant


Technical data

FESTO

Dimensions – CRHD- ... -MQ

Download CAD data → www.festo.com/en/engineering

Bearing cap with male thread



1 Regulating screw for end-position cushioning

+ = plus stroke length

Ø	α	AM	B Ø h9	BE	BF	BG	D Ø	EE	KK	L1
[mm]										
32	50°	22	30	M30x1.5	25	8	36	G $\frac{1}{8}$	M10x1.25	30
40	45°	24	38	M38x1.5	29	8	45	G $\frac{1}{8}$	M12x1.25	35
50	45°	32	45	M45x1.5	30	8	55	G $\frac{1}{4}$	M16x1.5	38
63	45°	32	45	M45x1.5	30	10	68	G $\frac{3}{8}$	M16x1.5	38
80	45°	40	50	M50x2	30	15	86	G $\frac{3}{8}$	M20x1.5	38
100	45°	40	50	M50x2	30	15	106	G $\frac{3}{8}$	M20x1.5	38

Ø	L7	MM Ø	RD Ø	RT	PL1	PL2	TG	VD	WF	ZJ	⌀1
[mm]											
32	5	12	27	M5	13	21	22	7	38	120	10
40	8	16	35	M6	15	18	30	7	45	135	13
50	5	20	42	M6	15	19	39	6.25	50	143	17
63	8	20	42	M8	17	24	49	6.25	50	158	17
80	9	25	47	M10	18	31	65	7.5	50	174	22
100	13	25	47	M10	22	30	82	7.5	50	189	22

Cylinders with piston rods
Corrosion-resistant cylinders

2.7

Round cylinders CRHD, corrosion-resistant


Technical data

FESTO

Dimensions – CRHD- ... -MC

Download CAD data → www.festo.com/en/engineering


End cap with yoke



Dimensions – CRHD- ... -MS

Download CAD data → www.festo.com/en/engineering

End cap with lug



Ø	CB	CD	CE	EW	L	MR	PL3	PL4	UB	UC	WH	XC
[mm]	+0.2/+0.1	Ø H9	Ø e8	-0.1/-0.2					-0.1/-0.2			
32	10	10	10	10	15	12	43	28	26	35	8	142
40	12	12	12	12	16	14	40	27	32	43	10	160
50	16	12	12	16	16	14	53	30	40	51	12	170
63	16	16	16	16	22	18	55	34	40	53	12	190
80	20	16	16	20	22	20	56	45	60	73	12	210
100	20	20	20	20	27	25	60	43.5	60	73	12	230

Round cylinders CRHD, corrosion-resistant

Technical data


FESTO

Ordering data				
Type	Piston Ø [mm]	Stroke [mm]	Part No.	Type
MQ – Bearing cap with male thread				
	32	10 ... 500	195 507	CRHD-32-...-PPV-A-MQ
	40		195 508	CRHD-40-...-PPV-A-MQ
	50		195 509	CRHD-50-...-PPV-A-MQ
	63		195 510	CRHD-63-...-PPV-A-MQ
	80		195 511	CRHD-80-...-PPV-A-MQ
	100		195 512	CRHD-100-...-PPV-A-MQ
S6 – Heat resistant up to 120 °C				
	32	10 ... 500	195 543	CRHD-32-...-PPV-A-MQ-S6
	40		195 544	CRHD-40-...-PPV-A-MQ-S6
	50		195 545	CRHD-50-...-PPV-A-MQ-S6
	63		195 546	CRHD-63-...-PPV-A-MQ-S6
	80		195 547	CRHD-80-...-PPV-A-MQ-S6
	100		195 548	CRHD-100-...-PPV-A-MQ-S6
MC – End cap with yoke (pivot pin and lock included in the scope of delivery)				
	32	10 ... 500	195 513	CRHD-32-...-PPV-A-MC
	40		195 514	CRHD-40-...-PPV-A-MC
	50		195 515	CRHD-50-...-PPV-A-MC
	63		195 516	CRHD-63-...-PPV-A-MC
	80		195 517	CRHD-80-...-PPV-A-MC
	100		195 518	CRHD-100-...-PPV-A-MC
S6 – Heat resistant up to 120 °C				
	32	10 ... 500	195 549	CRHD-32-...-PPV-A-MC-S6
	40		195 550	CRHD-40-...-PPV-A-MC-S6
	50		195 551	CRHD-50-...-PPV-A-MC-S6
	63		195 552	CRHD-63-...-PPV-A-MC-S6
	80		195 553	CRHD-80-...-PPV-A-MC-S6
	100		195 554	CRHD-100-...-PPV-A-MC-S6
MS – End cap with lug				
	32	10 ... 500	195 519	CRHD-32-...-PPV-A-MS
	40		195 520	CRHD-40-...-PPV-A-MS
	50		195 521	CRHD-50-...-PPV-A-MS
	63		195 522	CRHD-63-...-PPV-A-MS
	80		195 523	CRHD-80-...-PPV-A-MS
	100		195 524	CRHD-100-...-PPV-A-MS
S6 – Heat resistant up to 120 °C				
	32	10 ... 500	195 555	CRHD-32-...-PPV-A-MS-S6
	40		195 556	CRHD-40-...-PPV-A-MS-S6
	50		195 557	CRHD-50-...-PPV-A-MS-S6
	63		195 558	CRHD-63-...-PPV-A-MS-S6
	80		195 559	CRHD-80-...-PPV-A-MS-S6
	100		195 560	CRHD-100-...-PPV-A-MS-S6

Standard cylinders CRDSNU to ISO 6432, corrosion-resistant


Peripherals overview

FESTO



Variant

CRDSNU-S2




Mounting options

Threaded mounting

Mounting with hex nut

Swivel mounting at the rear



Mounting attachments and accessories

	Brief description	→ Page
1 Rod eye CRSGS	With spherical bearing	1 / 2.8-9
2 Rod clevis CRSG	Permits a swivelling movement of the cylinder in one plane	1 / 2.8-9
3 Foot mounting CRHBN	For bearing and end cap	1 / 2.8-1
4 Flange mounting CRFBN	For bearing or end cap	1 / 2.8-3
5 Clevis foot CRLBN	For direct mounting on end cap	1 / 2.8-6
6 Proximity sensor CRSMEO-4	With LED for operating status indication	1 / 2.8-9
7 Mounting kit CRSMBR	For proximity sensor CRSMEO-4	1 / 2.8-9
8 One-way flow control valve CRGRLA	For speed regulation	1 / 2.8-9
9 Push-in/threaded fitting CRQS	For connecting compressed air tubing with standard O.D.	Volume 3

Standard cylinders CRDSNU to ISO 6432, corrosion-resistant



Type code


		CRDSNU	–	25	–	80	–	P	–	A	–	S2
Type												
Double-acting												
CRDSNU	Standard cylinder											
Piston Ø [mm]												
Stroke [mm]												
Cushioning												
P	Non-adjustable at both ends											
Sensing												
A	Position sensing											
Variant												
S2	Through piston rod											

Standard cylinders CRDSNU to ISO 6432, corrosion-resistant

FESTO

Technical data

Function



Variants



S2

- Ø - Diameter
12 ... 25
- I - Stroke length
10 ... 500



DIN



General technical data				
Piston Ø	12	16	20	25
Pneumatic connection	M5	M5	G1/8	G1/8
Piston rod thread	M6	M6	M8	M10x1.25
Constructional design	Piston			
	Piston rod			
	Cylinder barrel			
Cushioning	Non-adjustable at both ends			
Position sensing	For proximity sensing			
Type of mounting	With accessories			
	With male thread			
Mounting position	Any			

Operating and environmental conditions				
Piston Ø	12	16	20	25
Operating medium	Filtered compressed air, lubricated or unlubricated			
Operating pressure [bar]	1 ... 10			
Ambient temperature ¹⁾ [°C]	-20 ... +80			
Corrosion resistance class CRC ²⁾	4			

¹⁾ Note operating range of proximity sensors

²⁾ Corrosion resistance class 4 according to Festo standard 940 070

Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required

Forces [N] and impact energy [J]				
Piston Ø	12	16	20	25
Theoretical force at 6 bar, advancing	68	121	189	295
Theoretical force at 6 bar, retracting	51	104	158	247
Max. impact energy at end positions	0.07	0.15	0.20	0.30



Pneumatic sizing using Pro Pneu
www.festo.com/en/engineering

Standard cylinders CRDSNU to ISO 6432, corrosion-resistant


Technical data



Weights [g]				
Piston Ø	12	16	20	25
Basic weight at 0 mm stroke	120	150	320	450
Additional weight per 10 mm stroke	4.2	4.8	7.2	10

Materials

Sectional view



Cylinder		
1	Piston rod	High-alloy stainless steel
2	Bearing cap	High-alloy stainless steel
3	Cylinder barrel	High-alloy stainless steel
4	End cap	High-alloy stainless steel
-	Seals	Polyurethane

Standard cylinders CRDSNU to ISO 6432, corrosion-resistant


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com/en/engineering


Basic version



+ plus stroke length

Variant

S2 – Through piston rod



+ plus stroke length
++ plus 2 stroke lengths

Ø	AM	B	BE	BF	CD	D	D4	EE	EW	G	KK	KV
[mm]												
12	16	16	M16x1.5	17	6	20	13.3	M5	12	10	M6	24
16	16	16	M16x1.5	17	6	20	17.3	M5	12	10	M6	24
20	20	22	M22x1.5	20	8	30	21.3	G $\frac{1}{8}$	16	16	M8	32
25	22	22	M22x1.5	22	8	30	26.5	G $\frac{1}{8}$	16	16	M10x1.25	32

Ø	KW	MM	L	L2	L5	PL	VD	WF	XC	ZJ	ZM	⌀1
[mm]												
12	8	6	9	50	16	6	2	22	75	72	94	5
16	8	6	9	56	16	6	2	22	82	78	100	5
20	11	8	12	68	19	8.2	2	24	95	92	116	7
25	11	10	12	69.5	21	8.2	2	28	104	97.5	125.4	9

Standard cylinders CRDSNU to ISO 6432, corrosion-resistant

FESTO


Technical data

Ordering data				
Variant	Piston Ø [mm]	Stroke [mm]	Part No.	Type
Basic version				
	12	10 ... 200	160 880	CRDSNU-12-...-P-A
	16	10 ... 200	160 881	CRDSNU-16-...-P-A
	20	10 ... 320	160 882	CRDSNU-20-...-P-A
	25	10 ... 500	160 883	CRDSNU-25-...-P-A
S2 – Through piston rod				
	12	10 ... 200	185 289	CRDSNU-12-...-P-A-S2
	16	10 ... 200	185 290	CRDSNU-16-...-P-A-S2
	20	10 ... 320	185 291	CRDSNU-20-...-P-A-S2
	25	10 ... 500	185 292	CRDSNU-25-...-P-A-S2

Standard cylinders CRDNG to ISO 15552, corrosion-resistant


Peripherals overview

FESTO



Variant

CRDNG-S2




Mounting options

CRDNG

Mounting at front

Mounting at rear


Mounting from below



CRDNGS

Mounting at front

Mounting on swivel flange



Standard cylinders CRDNG to ISO 15552, corrosion-resistant

Peripherals overview

FESTO

Mounting attachments and accessories				
	Brief description	CRDNG	CRDNGS	→ Page
1	Flange mounting CRFNG	■	–	1 / 2.8-4
2	Rod eye CRSGS	■	■	1 / 2.8-9
3	Rod clevis CRSG	■	■	1 / 2.8-9
4	Foot mounting CRHNC	■	–	1 / 2.8-2
5	Trunnion flange CRZNG	■	–	1 / 2.8-5
6	Trunnion support CRLNZG	■	–	1 / 2.8-5
7	Clevis foot CRLNG	–	■	1 / 2.8-6
8	Proximity sensor CRSMEO-4	■	■	1 / 2.8-9
9	Mounting kit CRSMB	■	■	1 / 2.8-9
10	One-way flow control valve CRGRLA	■	■	1 / 2.8-9
11	Push-in/threaded fittings CRQS	■	■	Volume 3

Standard cylinders CRDNG to ISO 15552, corrosion-resistant

FESTO

Type code

CRDNG – 50 – 80 – PPV – A – S2

Type

Double-acting

CRDNG Standard cylinder

CRDNGS Standard cylinder with swivel flange

Piston Ø [mm]

Stroke [mm]

Cushioning

PPV Adjustable at both ends

Sensing

A Position sensing

Variant

S2 Through piston rod


S6 Heat resistant up to 120 °C

Standard cylinders CRDNG to ISO 15552, corrosion-resistant

FESTO

Technical data

Function



- Diameter
32 ... 125
- Stroke length
10 ... 2000
- www.festo.com/en/Spare_parts_service

Wearing parts kits
→ 1 / 2.7-37

Variants




S2



S6

The variant S6 is not suitable for direct contact with food products because of the seals and the grease used.



CRDNG

CRDNGS

Conforms to

- ISO 15552
- ISO 6431
- VDMA 24562
- NFE 49003.1
- UNI 10290



DIN



General technical data							
Piston Ø	32	40	50	63	80	100	125
Pneumatic connection	G $\frac{1}{8}$	G $\frac{1}{4}$	G $\frac{1}{4}$	G $\frac{3}{8}$	G $\frac{3}{8}$	G $\frac{1}{2}$	G $\frac{1}{2}$
Piston rod thread	M10x1.25	M12x1.25	M16x1.5	M16x1.5	M20x1.5	M20x1.5	M27x2
Constructional design	Piston						
	Piston rod						
	Cylinder barrel						
Cushioning	Adjustable at both ends						
Cushioning length [mm]	20	20	23	23	30	30	40
Position sensing	For proximity sensing						
Type of mounting	With accessories						
	With female thread						
Mounting position	Any						

Operating and environmental conditions		
Variant	CRDNG/CRDNGS	S6
Operating medium	Filtered compressed air, lubricated or unlubricated	
Operating pressure	0.6 ... 10 bar	
Ambient temperature ¹⁾ [°C]	-20 ... +80	0 ... +120
Corrosion resistance class CRC ²⁾	4	

1) Note operating range of proximity sensors

2) Corrosion resistance class 4 according to Festo standard 940 070

Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required

Forces [N]							
Piston Ø	32	40	50	63	80	100	125
Theoretical force at 6 bar, advancing	482	753	1 178	1 870	3 015	4 712	7 360
Theoretical force at 6 bar, retracting	415	633	990	1 682	2 720	4 418	6 880

Standard cylinders CRDNG to ISO 15552, corrosion-resistant


Technical data

FESTO


Weights [g]							
Piston Ø	32	40	50	63	80	100	125
CRDNG							
Basic weight at 0 mm stroke	1 045	1 360	2 160	3 455	5 935	8 070	
Additional weight per 10 mm stroke	20	30	60	60	100	110	
CRDNGS							
Basic weight at 0 mm stroke	1 070	1 460	2 330				
Additional weight per 10 mm stroke	20	30	60				

Materials

Sectional view CRDNG



Sectional view CRDNGS



Cylinder	CRDNG/CRDNGS	S6
1 Piston rod	High-alloy stainless steel	
2 Bearing cap	Stainless steel casting	
3 Cylinder barrel	High-alloy stainless steel	
4 End cap	Stainless steel casting	
– Tie rod	High-alloy stainless steel	
– Seals	Polyurethane, nitrile rubber	Fluorocarbon rubber

Standard cylinders CRDNG to ISO 15552, corrosion-resistant


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com/en/engineering

CRDNG




- 1 Socket head screw with female thread
- 2 Cover for adjustable end-position cushioning
- 3 Threaded hole for direct mounting

+ plus stroke length

Variant

Download CAD data → www.festo.com/en/engineering

S2 – Through piston rod



+ plus stroke length
++ plus 2 stroke lengths

Ø	AM	B Ø e11	BG	D1	D4 Ø	D5 Ø	E	EE	J2	J3	KK	L1	L2
[mm]													
32	22	30	16	M6	33.6	6	50	G1/8	7	5.7	M10x1.25	16	94 +0.4
40	24	35	16	M6	41.6	6	55	G1/4	10	6.5	M12x1.25	18	105 +0.4/-0.6
50	32	40	16	M8	52.4	8	65	G1/4	11.5	8.6	M16x1.5	25	106 +0.4/-0.6
63	32	45	16	M10	65.4	8	75	G3/8	14.5	12	M16x1.5	25	121 +0.4/-0.6
80	40	45	23	M10	82.8	10	100	G3/8	15	13	M20x1.5	31	128 +0.4/-0.6
100	40	55	23	M12	102.8	10	120	G1/2	23	14	M20x1.5	36	138 +0.4/-0.6
125	54	60	23	M12	128.6	12	145	G1/2	28.5	8	M27x2	31	160 +0.4/-0.6

Ø	L3	L7	MM Ø	PL	RT	T1	TG	VA	VD	WH	ZJ	ZM	≈C1	≈C3
[mm]														
32	13	5.3	12	13	M6	9	32.5	4	5	26	120	148	10	6
40	16.5	2.5	16	14	M6	9	38	4	5	30	135	167	13	6
50	21	4.5	20	14	M8	10	46.5	4	5	37	143	183	17	8
63	22	5	20	18	M8	12	56.5	4	5	37	158	199	17	8
80	22.5	6	25	17	M10	15	72	4	5	46	174	222	22	10
100	22.5	9	25	18	M10	18	89	4	5	51	189	240	22	10
125	23.5	4.5	32	27	M12	18	110	6	6	66	226	292	27	12


Cylinders with piston rods
Corrosion-resistant cylinders

2.7

Standard cylinders CRDNG to ISO 15552, corrosion-resistant

FESTO

Technical data



Ø	CB	CD	L	MR	UB	XC
[mm]	H14	Ø H9				
32	26	10	18	9	45	142
40	28	12	21	10	52	160
50	32	12	23	11	60	170
63	40	16	28	13	70	190
80	50	16	32	13	90	210
100	60	20	37	17	110	230
125	70	25	44	23	130	276

Standard cylinders CRDNG to ISO 15552, corrosion-resistant

FESTO

Technical data

Ordering data				
Variant	Piston Ø [mm]	Stroke [mm]	Part No.	Type
CRDNG				
	32	10 ... 2000	160 884	CRDNG-32-...-PPV-A
	40	10 ... 2000	160 885	CRDNG-40-...-PPV-A
	50	10 ... 2000	160 886	CRDNG-50-...-PPV-A
	63	10 ... 2000	160 887	CRDNG-63-...-PPV-A
	80	10 ... 2000	160 888	CRDNG-80-...-PPV-A
	100	10 ... 2000	160 889	CRDNG-100-...-PPV-A
	125	10 ... 2000	185 280	CRDNG-125-...-PPV-A
S6 – Heat resistant up to 120 °C				
	32	10 ... 2000	185 293	CRDNG-32-...-PPV-A-S6
	40	10 ... 2000	185 294	CRDNG-40-...-PPV-A-S6
	50	10 ... 2000	185 295	CRDNG-50-...-PPV-A-S6
	63	10 ... 2000	185 296	CRDNG-63-...-PPV-A-S6
	80	10 ... 2000	185 297	CRDNG-80-...-PPV-A-S6
	100	10 ... 2000	185 298	CRDNG-100-...-PPV-A-S6
	125	10 ... 2000	185 299	CRDNG-125-...-PPV-A-S6
S2 – Through piston rod				
	32	10 ... 2000	185 282	CRDNG-32-...-PPV-A-S2
	40	10 ... 2000	185 283	CRDNG-40-...-PPV-A-S2
	50	10 ... 2000	185 284	CRDNG-50-...-PPV-A-S2
	63	10 ... 2000	185 285	CRDNG-63-...-PPV-A-S2
	80	10 ... 2000	185 286	CRDNG-80-...-PPV-A-S2
	100	10 ... 2000	185 287	CRDNG-100-...-PPV-A-S2
	125	10 ... 2000	185 288	CRDNG-125-...-PPV-A-S2
CRDNGS				
	32	10 ... 2000	160 890	CRDNGS-32-...-PPV-A
	40	10 ... 2000	160 891	CRDNGS-40-...-PPV-A
	50	10 ... 2000	160 892	CRDNGS-50-...-PPV-A
	63	10 ... 2000	160 893	CRDNGS-63-...-PPV-A
	80	10 ... 2000	160 894	CRDNGS-80-...-PPV-A
	100	10 ... 2000	160 895	CRDNGS-100-...-PPV-A
	125	10 ... 2000	185 281	CRDNGS-125-...-PPV-A
S6 – Heat resistant up to 120 °C				
	32	10 ... 2000	185 300	CRDNGS-32-...-PPV-A-S6
	40	10 ... 2000	185 301	CRDNGS-40-...-PPV-A-S6
	50	10 ... 2000	185 302	CRDNGS-50-...-PPV-A-S6
	63	10 ... 2000	185 303	CRDNGS-63-...-PPV-A-S6
	80	10 ... 2000	185 304	CRDNGS-80-...-PPV-A-S6
	100	10 ... 2000	185 305	CRDNGS-100-...-PPV-A-S6
	125	10 ... 2000	185 306	CRDNGS-125-...-PPV-A-S6

Ordering data – Wearing parts kits				
Piston Ø [mm]	Part No.	Type	Piston Ø [mm]	Part No. Type
32	125 713	CRDNG/S-32-...-PPV-A ¹⁾	63	125 716 CRDNG/S-63-...-PPV-A ¹⁾
40	125 714	CRDNG/S-40-...-PPV-A ¹⁾	80	125 717 CRDNG/S-80-...-PPV-A ¹⁾
50	125 715	CRDNG/S-50-...-PPV-A ¹⁾	100	125 718 CRDNG/S-100-...-PPV-A ¹⁾

1) Assembly grease included in scope of delivery.

Cylinders with piston rods
Corrosion-resistant cylinders

2.7

Accessories for corrosion-resistant cylinders

Technical data

FESTO

Foot mounting CRHBN

Scope of delivery:


CRHBN-... x1: 1 foot

CRHBN-... x2: 2 feet, 1 nut

Material:

High-alloy steel

Free of copper, PTFE and silicone



Dimensions and ordering data												
For Ø	AB Ø	AH	AO	AT	AU	R1	TR	US	XS	CRC ¹⁾	Weight [g]	Part No. Type
[mm]												
12	5.5	20	6	4	12.5	13	32	42	32	4	40	161 866 CRHBN-12/16x1
16	5.5	20	6	4	12.5	13	32	42	32	4	97	162 999 CRHBN-12/16x2
20	6.6	25	8	5	15	20	40	54	36	4	55	161 867 CRHBN-20/25x1
25	6.6	25	8	5	15	20	40	54	40	4	100	162 998 CRHBN-20/25x2

1) Corrosion resistance class 4 according to Festo standard 940 070


Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required.

Foot mounting CRH

Material:

High-alloy steel

Free of copper, PTFE and silicone



Dimensions and ordering data																
For Ø	AB Ø	AH	AO	AT	AU	H1	SA	TF	TR	US	XA	XS	CRC ¹⁾	Weight	Part No.	Type
[mm]														[g]		
32	7	28	7	4	14	14	124	28	52	66	148	48	4	237	162 951	CRH-32
40	9	33	10	5	20	18	153	30	60	80	178	60	4	341	162 952	CRH-40
50	9	40	10	6	20	20	160	40	70	90	190	64	4	559	162 953	CRH-50
63	9	45	10	6	20	20	164	50	76	96	195	64	4	680	162 954	CRH-63

1) Corrosion resistance class 4 according to Festo standard 940 070

Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required.


Accessories for corrosion-resistant cylinders

Technical data



Foot mounting CRHNC

Material:
High-alloy steel
Free of copper, PTFE and silicone



Dimensions and ordering data													
For Ø	AB Ø	AH	AO	AT	AU	SA	TR	US	XA	XS	CRC ¹⁾	Weight	Part No. Type
[mm]												[g]	
32	7	32	6.5	4	24	142	32	45	144.7	45.7	4	135	176 937 CRHNC-32
40	10	36	9	4	28	160.8	36	54	163.6	53.8	4	180	176 938 CRHNC-40
50	10	45	9.5	5	31	167.9	45	64	175	63.1	4	325	176 939 CRHNC-50
63	10	50	12.5	5	32	184.9	50	75	191.5	64.6	4	405	176 940 CRHNC-63
80	12	63	15	6	41	209.9	63	93	215.5	81.6	4	820	176 941 CRHNC-80
100	14.5	71	17.5	6	41	220.1	75	110	229.6	85.5	4	1,000	176 942 CRHNC-100
125	16.5	90	22	8	45	250	90	131	270	102	4	1,840	176 943 CRHNC-125

1) Corrosion resistance class 4 according to Festo standard 940 070
Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required.


Accessories for corrosion-resistant cylinders

Technical data

FESTO

Flange mounting CRFBN

Material:
High-alloy steel
Free of copper, PTFE and silicone




Dimensions and ordering data										
For Ø	FB	MF	TF	UF	UR	W	CRC ¹⁾	Weight	Part No.	Type
[mm]	Ø							[g]		
12, 16	5.5	4	40	53	30	18	4	25	161 864	CRFBN-12/16
20, 25	6.6	5	50	66	40	19	4	45	161 865	CRFBN-20/25

1) Corrosion resistance class 4 according to Festo standard 940 070
Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required.

Flange mounting CRFV

Material:
High-alloy steel
Free of copper, PTFE and silicone



Dimensions and ordering data														
For Ø	AB Ø	AH	AO	AT	AU	H1	TF	TR	US	XS	CRC ¹⁾	Weight	Part No.	Type
[mm]												[g]		
32	7	28	7	4	14	14	28	52	66	48	4	102	161 858	CRFV-32
40	9	33	10	5	19	18	30	60	80	60	4	190	161 859	CRFV-40
50	9	40	10	6	19	20	40	70	90	64	4	290	161 860	CRFV-50
63	9	45	10	6	19	20	50	76	96	64	4	365	161 861	CRFV-63

1) Corrosion resistance class 4 according to Festo standard 940 070
Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required.



Accessories for corrosion-resistant cylinders

Technical data



Flange mounting CRFNG

Material:
High-alloy steel
Free of copper, PTFE and silicone



Dimensions and ordering data											
For Ø	E	FB Ø	MF	R	TF	UF	W	CRC ¹⁾	Weight [g]	Part No.	Type
[mm]											
32	45	7	10	32	64	80	16	4	240	161 846	CRFNG-32
40	54	9	10	36	72	90	20	4	300	161 847	CRFNG-40
50	65	9	12	45	90	110	25	4	550	161 848	CRFNG-50
63	75	9	12	50	100	120	25	4	710	161 849	CRFNG-63
80	93	12	16	63	126	150	30	4	1,680	161 850	CRFNG-80
100	110	14	16	75	150	175	35	4	2,450	161 851	CRFNG-100
125	132	16	20	90	180	210	45	4	3,660	185 363	CRFNG-125

1) Corrosion resistance class 4 according to Festo standard 940 070
Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required.


Accessories for corrosion-resistant cylinders

Technical data

FESTO

Trunnion flange CRZNG

Material:
High-alloy steel
Free of copper, PTFE and silicone





Dimensions and ordering data												
For Ø	C2	C3	TD Ø e9	TK	TL	TM	UW	XH	XL	CRC ¹⁾	Weight	Part No. Type
[mm]											[g]	
32	71	86	12	16	12	50	50	18	128	4	150	161 852 CRZNG-32
40	87	105	16	20	16	63	55	20	145	4	260	161 853 CRZNG-40
50	99	117	16	24	16	75	65	25	155	4	430	161 854 CRZNG-50
63	116	136	20	24	20	90	75	25	170	4	640	161 855 CRZNG-63
80	136	156	20	28	20	110	100	32	188	4	1,300	161 856 CRZNG-80
100	164	189	25	38	25	132	120	32	208	4	2,400	161 857 CRZNG-100
125	192	217	25	50	25	160	150	40	250	4	3,600	185 362 CRZNG-125

- 1) Corrosion resistance class 4 according to Festo standard 940 070
Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required.

Trunnion support CRLNZG

Material:
High-alloy steel
Free of copper, PTFE and silicone



Dimensions and ordering data												
For Ø	CR Ø	FK Ø	FN	FS	H1	HB Ø H13	NH	TH ±0.2	UL	CRC ¹⁾	Weight	Part No. Type
[mm]	D11	±0.1									[g]	
32	12	15	30	10.5	15	6.6	18	32	46	4	200	161 874 CRLNZG-32
40, 50	16	18	36	12	18	9	21	36	55	4	330	161 875 CRLNZG-40/50
63, 80	20	20	40	13	20	11	23	42	65	4	440	161 876 CRLNZG-63/80
100/125	25	25	50	16	24.5	14	28.5	50	75	4	740	161 877 CRLNZG-100/125

- 1) Corrosion resistance class 4 according to Festo standard 940 070
Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required.


Accessories for corrosion-resistant cylinders

Technical data

FESTO

Clevis foot CRLBN

Material:
High-alloy steel
Free of copper, PTFE and silicone




Dimensions and ordering data													
For Ø	CM	EK Ø	FL	GL	HB	LE	MR	RG	UX	CRC ¹⁾	Weight [g]	Part No.	Type
[mm]													
12, 16	12.1	6	27 +0.3/-0.2	13	5.5	24	7	15	25	4	55	161 862	CRLBN-12/16
20, 25	16.1	8	30 +0.4/-0.2	16	6.6	26	10	20	32	4	62	161 863	CRLBN-20/25
32	16.1	10	35 +0.4/-0.2	18.5	6.6	31	11	24	35	4	107	195 866	CRLBN-32
40	18.1	12	40 +0.4/-0.2	24.5	9	35	13	30	45	4	184	195 867	CRLBN-40
50, 63	21.1	16	45 +0.5/-0.2	28	9	39	14	34	50	4	289	195 868	CRLBN-50/63

- 1) Corrosion resistance class 4 according to Festo standard 940 070
Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required.

Clevis foot mounting CRLNG

Material:
High-alloy steel
Free of copper, PTFE and silicone



Dimensions and ordering data															
For Ø	BR	BT	CK Ø	EB Ø	EM	GL	HB Ø	OF	PH	RA	TE	UL	UR	CRC ¹⁾	Weight [g]
[mm]			D11	H13	-0.4		H13								
32	10	8	10	-	25.8	21	6.6	-	32	18	38	51	31	4	120
40	11	10	12	-	27.8	24	6.6	-	36	22	41	54	35	4	160
50	12	12	12	-	31.8	33	9	-	45	30	50	65	45	4	280
63	15	12	16	15	39.8	37	9	10.8	50	35	52	67	50	4	375
80	15	14	16	18	49.8	47	11	12.7	63	40	66	86	60	4	580
100	19	15	20	18	59.8	55	11	13.7	71	50	76	96	70	4	935
125	22	20	25	20	69.8	70	14	18.6	90	60	94	124	90	4	2,530

- 1) Corrosion resistance class 4 according to Festo standard 940 070
Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required.


Accessories for corrosion-resistant cylinders

Technical data

FESTO

Clevis foot CRSBS

Material:
High-alloy steel



Dimensions and ordering data											
For Ø	CK	CM	D1	D2	FL	GL	H1	HB	L3	L4	LE
[mm]	Ø H8/f7		Ø					Ø			
32	10	38.1	15	M8x1	35	20	4	7	14.5	6.5	31
40	12	46.1	20	M10x1	40	27	5	9	18.5	9	36
50	14	57.1	23	M12x1.5	45	30	6	9	23	12	39
63	16	70.4	23	M14x1.5	50	34	6	9	29	16	44


For Ø	MR	RF	RG	UK	UX	≈C1	CRC ¹⁾	Weight	Part No.	Type
[mm]								[g]		
32	12	20	24	50.1	40	5	4	130	162 955	CRSBS-32
40	13	28	30	60.1	50	6	4	200	162 956	CRSBS-40
50	14	36	34	74.1	54	6	4	310	162 957	CRSBS-50
63	15	42	35	88.1	65	8	4	440	162 958	CRSBS-63

1) Corrosion resistance class 4 according to Festo standard 940 070
Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required

Pivot bolt CRGBS

For swivel mounting

Material:
High-alloy steel
Free of copper, PTFE and silicone



Dimensions and ordering data								
For Ø	D1	L1	L2	TD	≈C1	CRC ¹⁾	Weight	Part No. Type
[mm]				Ø f8			[g]	
32	M8x1	14.5	6.5 ±0.1	10	5	4	10	163 132 CRGBS-32
40	M10x1	18.5	9 ±0.1	12	6	4	20	163 133 CRGBS-40
50	M12x1.5	23	12 ±0.2	14	6	4	40	163 134 CRGBS-50
63	M14x1.5	29	16 ±0.2	16	8	4	65	163 135 CRGBS-63

1) Corrosion resistance class 4 according to Festo standard 940 070
Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required


Accessories for corrosion-resistant cylinders

Technical data

FESTO

Clevis foot CRLMC

Material:
High-alloy steel
Free of copper, PTFE and silicone





Dimensions and ordering data																	
For Ø	BR	BT	CK Ø	EB Ø	EM	GL	HB Ø	OF	PH	RA	TE	UL	UR	CRC ¹⁾	Weight	Part No.	Type
[mm]			D11	H13	−0.4		H13								[g]		
32	10	8	10	−	10	21	6.6	−	32	18	38	51	31	4	101	197 320	CRLMC-32
40	11	10	12	−	12	24	6.6	−	36	22	41	54	35	4	139	197 321	CRLMC-40
50	12	12	12	−	16	33	9	−	45	30	50	65	45	4	242	197 322	CRLMC-50
63	15	12	16	15	16	37	9	10.8	50	35	52	67	50	4	303	197 323	CRLMC-63
80	15	14	16	18	20	47	11	12.7	63	40	66	86	60	4	515	197 324	CRLMC-80
100	19	15	20	18	20	55	11	13.7	71	50	76	96	70	4	761	197 325	CRLMC-100

- 1) Corrosion resistance class 4 according to Festo standard 940 070
Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required

Ring nut CR

Material:
High-alloy steel
Free of copper, PTFE and silicone



Dimensions and ordering data								
For Ø	B1	D1	D2	D3	CRC ¹⁾	Weight	Part No.	Type
[mm]						[g]		
32	8	M30x1.5	42	36	4	40	197 326	CR-M30x1,5
40	10	M38x1.5	50	48	4	61	197 327	CR-M38x1,5
50, 63	10	M45x1.5	60	56	4	89	197 328	CR-M45x1,5
80, 100	13	M50x2	75	67	4	228	197 329	CR-M50x2

- 1) Corrosion resistance class 4 according to Festo standard 940 070
Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required.

Accessories for corrosion-resistant cylinders

Technical data

FESTO

Ordering data – Piston rod attachments				Technical data → 1 / 10.3-5			
	For Ø	Part No.	Type		For Ø	Part No.	Type
Rod eye CRSGS				Rod clevis CRSG			
	12, 16	195 580	CRSGS-M6		12, 16	13 567	CRSG-M6
	20	195 581	CRSGS-M8		20	13 568	CRSG-M8
	32	195 582	CRSGS-M10x1,25		32	13 569	CRSG-M10x1,25
	40	195 583	CRSGS-M12x1,25		40	13 570	CRSG-M12x1,25
	50, 63	195 584	CRSGS-M16x1,5		50, 63	13 571	CRSG-M16x1,5
	80, 100	195 585	CRSGS-M20x1,5		80, 100	13 572	CRSG-M20x1,5
	125	195 586	CRSGS-M27x2		125	185 361	CRSG-M27x2

Ordering data – Proximity sensor, magnetic reed				Technical data → 1 / 10.2-79			
	Electrical connection	Cable length		Part No.	Type		
	Cable	[m]					
	NO contact						
	Resistant to corrosion						
	3-wire	2.5		161 775	CRSME0-4-K-LED-24		

Ordering data – Mounting kit				Technical data → 1 / 10.2-81			
	For Ø	Part No.	Type		For Ø	Part No.	Type
Mounting kit CRSMBR				Mounting kit CRSMB			
	12	164 581	CRSMBR-12		32	161 763	CRSMB-32
	16	164 582	CRSMBR-16		40	161 764	CRSMB-40
	20	164 583	CRSMBR-20		50	161 765	CRSMB-50
	25	164 584	CRSMBR-25		63	161 766	CRSMB-63
	32	163 888	CRSMBR-32		80	161 767	CRSMB-80
	40	163 889	CRSMBR-40		100	161 768	CRSMB-100
	50	163 890	CRSMBR-50		125	185 365	CRSMB-125
	63	163 891	CRSMBR-63				

Ordering data – Proximity sensor, magneto-resistive				Technical data → 1 / 10.2-32			
	Switch output	Electrical connection	Cable length	Part No.	Type		
		Cable	[m]				
	NO contact						
	PNP	3-wire	2.5	525 563	CRSMT-8-PS-K2,5-LED-24		
			5.0	525 564	CRSMT-8-PS-K5-LED-24		

Ordering data – Mounting kit				Technical data → 1 / 10.2-51			
				Part No.	Type		
				525 565	CRSMB-8-32/100		

Ordering data – One-way flow control valves				Technical data → Volume 2			
	Connection		Material	Part No.	Type		
	Thread	For push-in fitting					
	M5	CRQS/CRQSL/CRQST	Electrolytically polished stainless steel casting	161 403	CRGRLA-M5-B		
	G1/8			161 404	CRGRLA-1/8-B		
	G1/4			161 405	CRGRLA-1/4-B		
	G3/8			161 406	CRGRLA-3/8-B		
	G1/2			161 407	CRGRLA-1/2-B		

Accessories for corrosion-resistant cylinders

Technical data

FESTO

Ordering data – Air reservoir					Technical data → Volume 3
	Connection	Volume [l]	Material	Part No.	Type
	Thread				
	G1/8	0.1	High-alloy stainless steel	160 233	CRVZS-0.1
	G1/4	0.4		160 234	CRVZS-0.4
	G1/4	0.75		160 235	CRVZS-0,75
	G1/2	2		160 236	CRVZS-2
	G1, G3/8	5		192 159	CRVZS-5
	G1, G3/8	10		160 237	CRVZS-10

Ordering data – Compressed air tubing			Technical data → Volume 3
	Standard O.D. tubing		PLN, PFAN