




- Fully assembled and tested drive unit
- Integrated multi-pin connection as interface to the PLC
- Rapid response times through direct connection of the valve and drive
- Integrated proximity sensors for position sensing

Cylinder/valve combination DNCV, standard port pattern

Key features

FESTO



Easy to assemble

- Fully assembled and tested drive unit
- Lower costs for ordering, installation and commissioning
- Direct mounting
- Integrated proximity sensors for position sensing
- Integrated exhaust air flow control

Compatible

- Comprehensive range of accessories from the standard cylinder modular system
- Multi-pin connection as interface to PLC, ASI module or CPX terminal (various bus protocols)
- Dimensions largely compliant with DIN ISO 6431 and VDMA 24 562

Flexible

- Integrated 5/2-way or 5/3-way valves
- Optional diagnostic module for monitoring of stroke duration and number of strokes

Reliable


- Status displays for piston position and valve actuation
- Rapid response times through direct connection of the valve and drive
- Adjustable pneumatic end-position cushioning
- Manual override

Cylinder/valve combination DNCV, standard port pattern

Key features

FESTO

High functionality



- | | | | |
|---|---|---|--|
| 1 Multi-pin connection, M12 plug, 8-pin | 5 Regulating screw for pneumatic end-position cushioning PPV | 7 Regulating screws for stroke speed, separated for forward and return stroke | 9 Diagnostic module (optional) with LEDs for displaying the piston position, valve switching status and for diagnosis of stroke duration and number of strokes |
| 2 Supply port (QS push-in fitting) | 6 Adjusting knob for fine adjustment of the position of the integrated proximity sensors (removable to prevent inadvertent resetting) | 8 Manual override, non-detenting or detenting | |
| 3 Silencer (QS push-in fitting for exhaust air) | | | |
| 4 Valve | | | |

Cylinder/valve combination DNCV, standard port pattern



Key features

Valve			
Circuit symbol	Description	Circuit symbol	Description
5/2L			
	5/2-way valve, single solenoid with spring return: The valve is normally closed, the piston rod retracts.		5/2-way valve, single solenoid with spring return: The valve is normally open, the piston rod advances.
5/2J			
	5/2-way valve, double solenoid (bistable valve): The valve does not have a defined normal position; instead it requires the electrical actuator or manual override for a defined switching status. The piston rod therefore retracts or advances in accordance with the current valve position.		5/3-way valve, pressurised in mid-position: The piston rod advances when the valve is in the normal position due to the differential piston areas.
5/3E			
	5/3-way valve, exhausted in mid-position: In the normal valve position, the piston rod is not subjected to any pressure forces; the piston rod can therefore be moved freely.		5/3-way valve, closed in mid-position: The piston rod is subjected to pressure when the valve is in the normal position and therefore remains in the current position. The piston rod may, however, drift when external forces are present; it is particularly important to be aware of this in the case of vertical cylinder configurations.
Manual override			
Function diagram	Description	Function diagram	Description
	Non-detenting actuation: The manual override is activated using a pointed object.		Detenting actuation: The manual override is actuated by moving the slide.

Cylinder/valve combination DNCV, standard port pattern

Key features

FESTO

Basic diagnosis

Proximity switch monitoring:

Display of the piston position (retracted or advanced end position).

The diagnostic LED lights up in the case of double signalling. The error signal is not output to the controller.

Diagnostic module DNCV-...-D (optional, expandable)

Proximity switch monitoring:

In the event of a malfunction or double signalling, apart from the diagnostic LED lighting up, the signal level at the diagnostic output also changes from 24 V to 0 V.

Monitoring of stroke duration:

The motion duration for the forward and return stroke is compared with a limit value that is pre-selected using DIP switches. This limit value can be adjusted in increments from 0.1 s to max. 6.3 s. If the limit value is exceeded, the diagnostic LED lights up and the signal level at the diagnostic output changes from 24 V to 0 V.

Monitoring of number of strokes:

The number of strokes is compared with a limit value that is pre-selected using DIP switches. This limit value can be adjusted in increments from 10,000 strokes to max. 630,000 strokes. If this limit value is exceeded, the diagnostic LED flashes and the signal level at the diagnostic output changes from 24 V to 0 V. This change in signal level can also be deactivated.




CPX connection

Support via a connection block equipped with four M12 sockets means that up to 4 cylinder/valve combinations with integrated proximity sensors can be connected. Two inputs and two outputs per socket are supported for each cylinder/valve combination. It is therefore possible to control max. 2 solenoid coils and record input signals from 2 proximity

sensors with a pre-assembled cable. Two inputs on two sockets are bridged to provide support for the diagnostic module of the cylinder/valve combination so that 2 cylinder/valve combinations with diagnostic modules can be connected.

Further information:
➔ Info 210




AS-interface®

Special interface module, configured for the cylinder/valve combination with integrated diagnostic module. This allows easy and flexible connection of the cylinder/valve combination in upstream applications to the AS-interface. Two inputs and two outputs as well as a diagnostic input on one 8-pin M12 socket.

Optimised design for cylinder/valve combination with integrated diagnostic module. Ready-to-connect cable KM12-8GD8GS-2-PU for Festo plug and work™ installation.


Further information:
➔ Info 220



Cylinder/valve combination DNCV, standard port pattern

Peripherals overview

FESTO



Cylinder/valve combination DNCV, standard port pattern

Peripherals overview

FESTO

Mounting attachments and accessories		
	Brief description	→ Page
1	Adapter kit DPNC	For connecting two cylinders DNCV with identical piston $\varnothing$ to form a multi-position cylinder
2	Foot mounting HNC	For bearing and end cap, corresponds to MS1 to DIN ISO 6431
3	Flange mounting FNC	For bearing or end cap, corresponds to MF1/MF2 to DIN ISO 6431
4	Trunnion flange ZNCF	For bearing or end cap
5	Trunnion supports LNZG	For trunnion flange ZNCF 4
6	Swivel flange SNC	For end cap
7	Clevis foot LSNG	With spherical bearing for swivel flange SNC 6
8	Clevis foot LSNSG	Weld-on, with spherical bearing for swivel flange SNC 6
9	Swivel flange SNCS	With spherical bearing for end cap
10	Clevis foot LBG	For swivel flange SNCS 9 or rod eye SGS 15
11	Swivel flange SNCB	For swivel flange SNCL 14 or for end cap, corresponds to MP2 to DIN ISO 6431
12	Clevis foot LNG	For swivel flange SNCB 11
13	Clevis foot LSN	With spherical bearing for swivel flange SNCB 11
14	Swivel flange SNCL	For end cap, corresponds to MP4 to DIN ISO 6431
15	Rod eye SGS	With spherical bearing
16	Clevis foot, lateral LQG	For rod eye SGS 15
17	Rod clevis SGA	With male thread for rod eye SGS 15
18	Coupling piece KSG	For compensating radial deviations
19	Rod clevis SG	
20	Self-aligning rod coupler FK	For compensating radial and angular deviations
21	Guide unit FENG	For protecting against torsion at high torque loads
22	Diagnostic module DNCV-...-D	
23	Silencer UC-QS-...H	
24	Connecting cable KM12-8GD8GS-2-PU	
25	Plug socket with cable SIM-M12-8GD-...-PU	

Cylinder/valve combination DNCV, standard port pattern

Type code

FESTO


DNCV		40	320	PPV	A	5/2L	D
Type							
Double-acting							
DNCV	Cylinder/valve combination						
Piston $\varnothing$ [mm]							
Stroke [mm]							
End-position cushioning							
PPV	Adjustable at both ends						
Position sensing							
A	Position sensing						
Valve variant							
5/2L	5/2-way valve, single solenoid, piston rod retracted						
5/2LA	5/2-way valve, single solenoid, piston rod advanced						
5/2J	5/2-way valve, double solenoid						
5/3B	5/3-way valve, mid-position pressurised						
5/3E	5/3-way valve, mid-position exhausted						
5/3G	5/3-way valve, mid-position closed						
Diagnostic module (optional)							
D	With diagnostic module						

Cylinder/valve combination DNCV, standard port pattern

FESTO

Technical data

Function¹⁾



- Ø - Diameter
32 ... 63 mm
- I - Stroke length
70 ... 500 mm
- T - www.festo.com/en/Spare_parts_service



1) E.g. with 5/2-way valve, single solenoid

General technical data				
Piston Ø	32	40	50	63
Cylinder				
Pneumatic connection	➔ Valve			
Piston rod thread	M10x1.25	M12x1.25	M16x1.5	M16x1.5
Operating medium	Filtered compressed air, lubricated or unlubricated			
Constructional design	Piston			
	Piston rod			
	Smooth profile barrel			
Cushioning	Adjustable at both ends			
Cushioning length [mm]	20	20	22	22
Max. speed ¹⁾ [m/s]	1.5	1.1	1.3	0.8
Position sensing	Via integrated proximity sensors			
Type of mounting	Via female thread			
	Via accessories			
Mounting position	Any			
Valve				
Pneumatic connection	QS-8	QS-8	QS-10	QS-10
Electrical connection	M12 plug, 8-pin			
Constructional design	Piston spool valve			
Operating voltage	24 V DC +10/-15%			
Power consumption	Pull: 1 W; hold: 0.5 W			
Switching position display	By means of integrated control electronics			
Manual override	Non-detenting/detenting			
Exhaust air flow control	Integrated			
Exhaust air	Ducted, common output 3/5 with silencer			
Silencer	UC-8	UC-8	UC-10	UC-10
Proximity sensor				
Mode of operation	Reed contact			
Type of mounting	Integrated in cylinder profile, can be adjusted using external adjusting knob			
Switching function	NO contact			
Electrical connection	Integrated conductive track			
Operating voltage	24 V DC +15/−25%			
Switching current	6 mA ≤ I ≤ 20 mA, short circuit proof			
Adjustment range	±10 mm in both end positions			
Repetition accuracy [mm]	±0.2			

1) retracting, with 5/2-way valve

Cylinder/valve combination DNCV, standard port pattern

Technical data

FESTO

Operating and environmental conditions				
Piston Ø	32	40	50	63
Operating pressure [bar]	3 ... 8			
Ambient temperature [°C]	-5 ... +50			
Corrosion resistance class CRC ¹⁾	2			
Protection class	IP65			

1) Corrosion resistance class 2 according to Festo standard 940 070


Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

Forces [N] and impact energy [J]				
Piston Ø	32	40	50	63
Theoretical force at 6 bar, advancing	483	754	1178	1870
Theoretical force at 6 bar, retracting	415	633	990	1682
Max. impact energy at the end positions	0.1	0.2	0.2	0.5



Pneumatic sizing using Pro Pneu
www.festo.com/en/engineering

Max. lateral force F_q as a function of the projection x



Cylinder/valve combination DNCV, standard port pattern


FESTO

Technical data

Weights [g]				
Piston Ø	32	40	50	63
Product weight with 0 mm stroke	900	1275	1960	2620
Additional weight per 10 mm stroke	36	49	79	88
Moving load with 0 mm stroke	162	307	538	663
Additional load per 10 mm stroke	9	16	25	25

Materials

Sectional view



Cylinder		
1	Cylinder barrel	Smooth anodised aluminium
2	Bearing/end caps	Anodised aluminium
3	Piston rod	High-alloy steel
4	Flange screws	Galvanised steel
5	Dynamic seals	Polyurethane
–	Static seals	Nitrile rubber
–	Lubricant	Klüberplex BE 31-222
Valve		
6	Housing	Coated aluminium
7	Covers	Polyacetate
–	Plug housing	Nickel-plated brass
–	Plug contacts	Gold-plated brass


Cylinder/valve combination DNCV, standard port pattern

Technical data

FESTO

Dimensions

Download CAD data → www.festo.com/en/engineering



- 1 Multi-pin connection, plug M12, 8-pin
 - 2 Supply port
 - 3 Silencer for exhaust air
 - 4 Regulating screw for pneumatic end-position cushioning PPV
 - 5 Adjusting knob for fine adjustment of the integrated proximity sensors
 - 6 Regulating screw for stroke speed
 - 7 Manual override, non-detenting/detenting
- + = plus stroke length







Ø [mm]	AM	B Ø d11	BG	D1 Ø	E	H1 ±0.5	H2 ±0.5	H3 ±0.5	H4 ±0.5	J1 ±0.5	J2 ±0.5	J3 ±0.5	J4 ±0.5	J5 ±0.5	J6 ±0.5	KK	L1
32	22	30	16	8	50	91	58	34	47	6	2	15	2	12	14	M10x1.25	19
40	24	35	16	8	58	99	66	38	85	6	2	15	2	12	14	M12x1.25	21
50	32	40	17	10	70	114	74	44	61	10	9	17	4	15	17	M16x1.5	27
63	32	45	17	10	81	125	85	49	67	10	9	17	4	15	17	M16x1.5	27

Ø [mm]	L2	L3 ±0.5	L4 ±0.5	L5 ±0.5	L6 ±0.5	L7 ±0.5	MM Ø	RT	TG	VA max.	VD max.	WH ±1.5	ZJ	⌀ 1	⌀ 2	⌀ 3
32	94 ±0.4	18	74	35	7	9	12	M6	32.5 ±0.5	4	4.5	26	120.7	10	17	6
40	104.8 ±0.5	23	75	35	7	14	16	M6	38 ±0.5	4	4	31	135.6	13	19	6
50	105.9 ±0.5	23	79	46	15	12	20	M8	46.5 ±0.6	4	5	38	144	17	24	8
63	120.9 ±0.5	29	81	46	9	15	20	M8	56.5 ±0.7	4	5	39	159.5	17	24	8

Cylinder/valve combination DNCV, standard port pattern

FESTO

Technical data

Ordering data – Cylinder/valve combination							
	Piston Ø	Stroke	Basic version		With diagnostic module		
	[mm]	[mm]	Part No.	Type	Part No.	Type	
With 5/2-way single solenoid valve, piston rod retracted in normal position							
	32	70 ... 500	196 796	DNCV-32-....-PPV-A-5/2L	196 816	DNCV-32-....-PPV-A-5/2LD	
	40	70 ... 500	196 797	DNCV-40-....-PPV-A-5/2L	196 817	DNCV-40-....-PPV-A-5/2LD	
	50	85 ... 500	196 798	DNCV-50-....-PPV-A-5/2L	196 818	DNCV-50-....-PPV-A-5/2LD	
	63	85 ... 500	196 799	DNCV-63-....-PPV-A-5/2L	196 819	DNCV-63-....-PPV-A-5/2LD	
With 5/2-way single solenoid valve, piston rod advanced in normal position							
	32	70 ... 500	536 424	DNCV-32-....-PPV-A-5/2LA	536 428	DNCV-32-....-PPV-A-5/2LAD	
	40	70 ... 500	536 425	DNCV-40-....-PPV-A-5/2LA	536 429	DNCV-40-....-PPV-A-5/2LAD	
	50	85 ... 500	536 426	DNCV-50-....-PPV-A-5/2LA	536 430	DNCV-50-....-PPV-A-5/2LAD	
	63	85 ... 500	536 427	DNCV-63-....-PPV-A-5/2LA	536 431	DNCV-63-....-PPV-A-5/2LAD	
With 5/2-way double solenoid valve							
	32	70 ... 500	196 800	DNCV-32-....-PPV-A-5/2J	196 820	DNCV-32-....-PPV-A-5/2JD	
	40	70 ... 500	196 801	DNCV-40-....-PPV-A-5/2J	196 821	DNCV-40-....-PPV-A-5/2JD	
	50	85 ... 500	196 802	DNCV-50-....-PPV-A-5/2J	196 822	DNCV-50-....-PPV-A-5/2JD	
	63	85 ... 500	196 803	DNCV-63-....-PPV-A-5/2J	196 823	DNCV-63-....-PPV-A-5/2JD	
With 5/3-way valve, mid-position pressurised							
	32	70 ... 500	196 804	DNCV-32-....-PPV-A-5/3B	196 824	DNCV-32-....-PPV-A-5/3BD	
	40	70 ... 500	196 805	DNCV-40-....-PPV-A-5/3B	196 825	DNCV-40-....-PPV-A-5/3BD	
	50	85 ... 500	196 806	DNCV-50-....-PPV-A-5/3B	196 826	DNCV-50-....-PPV-A-5/3BD	
	63	85 ... 500	196 807	DNCV-63-....-PPV-A-5/3B	196 827	DNCV-63-....-PPV-A-5/3BD	
With 5/3-way valve, mid-position exhausted							
	32	70 ... 500	196 808	DNCV-32-....-PPV-A-5/3E	196 828	DNCV-32-....-PPV-A-5/3ED	
	40	70 ... 500	196 809	DNCV-40-....-PPV-A-5/3E	196 829	DNCV-40-....-PPV-A-5/3ED	
	50	85 ... 500	196 810	DNCV-50-....-PPV-A-5/3E	196 830	DNCV-50-....-PPV-A-5/3ED	
	63	85 ... 500	196 811	DNCV-63-....-PPV-A-5/3E	196 831	DNCV-63-....-PPV-A-5/3ED	
With 5/3-way valve, mid-position closed							
	32	70 ... 500	196 812	DNCV-32-....-PPV-A-5/3G	196 832	DNCV-32-....-PPV-A-5/3GD	
	40	70 ... 500	196 813	DNCV-40-....-PPV-A-5/3G	196 833	DNCV-40-....-PPV-A-5/3GD	
	50	85 ... 500	196 814	DNCV-50-....-PPV-A-5/3G	196 834	DNCV-50-....-PPV-A-5/3GD	
	63	85 ... 500	196 815	DNCV-63-....-PPV-A-5/3G	196 835	DNCV-63-....-PPV-A-5/3GD	

Ordering data – Spare valves							
Piston Ø [mm]	Function	Part No.	Type	Piston Ø [mm]	Function	Part No.	Type
32/40	5/2L	647 106	DNCV-32/40,5/2L	50/63	5/2L	647 111	DNCV-50/63,5/2L
	5/2LA	672 235	DNCV-32/40,5/2LA		5/2LA	672 236	DNCV-50/63,5/2LA
	5/2J	647 107	DNCV-32/40,5/2J		5/2J	647 112	DNCV-50/63,5/2J
	5/3B	647 108	DNCV-32/40,5/3B		5/3B	647 113	DNCV-50/63,5/3B
	5/3E	647 109	DNCV-32/40,5/3E		5/3E	647 114	DNCV-50/63,5/3E
	5/3G	647 110	DNCV-32/40,5/3G		5/3G	647 115	DNCV-50/63,5/3G

Ordering data – Wearing parts kits		
Piston Ø [mm]	Part No.	Type
32	365 195	DNCV-32-PPV-A ¹⁾
40	365 196	DNCV-40-PPV-A ¹⁾
50	365 197	DNCV-50-PPV-A ¹⁾
63	365 198	DNCV-63-PPV-A ¹⁾

1) Assembly grease included in scope of delivery.

Cylinder/valve combination DNCV, standard port pattern

Accessories




Diagnostic module DNCV-...-D



Ordering data			
For Ø	Weight	Part No.	Type
[mm]	[g]		
32 ... 63	62.4	536 945	DNCV-...-D

Silencer UC-QS

Material:
Polyurethane



Dimensions and ordering data						
For Ø	D	D1	L	L1	Weight	Part No. Type
[mm]	Ø	Ø			[g]	
32/40	13.8	8	54.4	23.4	2.5	175 611 UC-QS-8H
50/63	17.8	10	68.7	26.7	5.2	526 475 UC-QS-10H

Cylinder/valve combination DNCV, standard port pattern

Accessories



Plug socket with cable SIM

Material:
Housing: Polyurethane
Cable sheath: Polyurethane



Ordering data			Technical data → Volume 2	
For Ø	Cable length	Weight	Part No.	Type
[mm]	[m]	[g]		
32 ... 63	2	147.9	525 616	SIM-M12-8GD-2-PU
	5	343.7	525 618	SIM-M12-8GD-5-PU

Connecting cable KM12


Material:
Housing: Polyurethane
Cable sheath: Polyurethane



Ordering data			Technical data → Volume 2	
For Ø	Cable length	Weight	Part No.	Type
[mm]	[m]	[g]		
32 ... 63	2	156.3	525 617	KM12-8GD8GS-2-PU

Terminal allocation

M12 plug socket



- | | | | |
|---|--------------------------|---|----------------------|
| 1 | 24 V sensor (white, WH) | 5 | Coil 14 (grey, GY) |
| 2 | Sensor 2 (brown, BN) | 6 | Coil 12 (pink, PK) |
| 3 | Sensor 1 (green, GN) | 7 | Diagnosis (blue, BU) |
| 4 | 0 V sensors (yellow, YE) | 8 | 0 V coils (red, RD) |


Cylinder/valve combination DNCV, standard port pattern



Accessories

Foot mounting HNC/CRHNC

Material:
HNC: Galvanised steel
CRHNC: High-alloy steel
Free of copper, PTFE and silicone



Dimensions and ordering data										
For Ø	AB Ø	AH	AO	AT	AU	SA	TR	US	XA	XS
[mm]										
32	7	32	6.5	4	24	142	32	45	144	45
40	10	36	9	4	28	161	36	54	163	53
50	10	45	9.5	5	31	170	45	64	175	62
63	10	50	12.5	5	32	185	50	75	190	63

For Ø	Basic version				High corrosion protection			
	CRC ¹⁾	Weight [g]	Part No.	Type	CRC ¹⁾	Weight [g]	Part No.	Type
[mm]								
32	2	135	174 369	HNC-32	4	135	176 937	CRHNC-32
40	2	180	174 370	HNC-40	4	180	176 938	CRHNC-40
50	2	325	174 371	HNC-50	4	325	176 939	CRHNC-50
63	2	405	174 372	HNC-63	4	405	176 940	CRHNC-63

1) Corrosion resistance class 2 according to Festo standard 940 070
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.
Corrosion resistance class 4 according to Festo standard 940 070
Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required.

Cylinder/valve combination DNCV, standard port pattern

FESTO

Accessories


Flange mounting FNC/CRFNG

Material:

FNC: Galvanised steel

CRFNG: High-alloy steel

Free of copper, PTFE and silicone



Dimensions and ordering data								
For Ø	E	FB Ø H13	MF	R	TF	UF	W	ZF
[mm]								
32	45	7	10	32	64	80	16	130.7
40	54	9	10	36	72	90	21	145.6
50	65	9	12	45	90	110	26	156
63	75	9	12	50	100	120	27	171.5

For Ø	Basic version				High corrosion protection			
	CRC ¹⁾	Weight [g]	Part No.	Type	CRC ¹⁾	Weight [g]	Part No.	Type
[mm]								
32	2	240	174 376	FNC-32	4	240	161 846	CRFNG-32
40	2	280	174 377	FNC-40	4	300	161 847	CRFNG-40
50	2	520	174 378	FNC-50	4	550	161 848	CRFNG-50
63	2	690	174 379	FNC-63	4	710	161 849	CRFNG-63

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

Corrosion resistance class 4 according to Festo standard 940 070

Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required.


Cylinder/valve combination DNCV, standard port pattern

Accessories



Swivel flange SNC

Material:
die-cast aluminium



Dimensions and ordering data											
For Ø	CG	CP	EK Ø	FL ±0.2	L	SR	XC	CRC ¹⁾	Weight [g]	Part No.	Type
[mm]	H14	h14									
32	14	34	10	22	13	10	142.7	2	90	174 383	SNC-32
40	16	40	12	25	16	12	160.6	2	120	174 384	SNC-40
50	21	45	16	27	16	12	171	2	240	174 385	SNC-50
63	21	51	16	32	21	16	191.5	2	320	174 386	SNC-63

1) Corrosion resistance class 2 according to Festo standard 940 070
Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

Cylinder/valve combination DNCV, standard port pattern

FESTO

Accessories


Swivel flange SNCB/SNCB-...-R3

Material:

SNCB: Die-cast aluminium

SNCB-...-R3: Die-cast aluminium,
protective coating, high corrosion
protection

Free of copper, PTFE and silicone



Dimensions and ordering data								
For Ø	CB	EK	FL	L	ML	MR	UB	XC
[mm]	H14	Ø e8	±0.2				h14	
32	26	10	22	13	55	10	45	142.7
40	28	12	25	16	63	12	52	160.6
50	32	12	27	16	71	12	60	171
63	40	16	32	21	83	16	70	191.5

For Ø	Weight	Basic version		Variant R3 – High corrosion protection	
		Part No.	Type	CRC ¹⁾	Part No. Type
32	100	174 390	SNCB-32	3	176 944 SNCB-32-R3
40	150	174 391	SNCB-40	3	176 945 SNCB-40-R3
50	225	174 392	SNCB-50	3	176 946 SNCB-50-R3
63	365	174 393	SNCB-63	3	176 947 SNCB-63-R3

1) Corrosion resistance class 3 according to Festo standard 940 070

Components requiring higher corrosion resistance. External visible parts in direct contact with industrial atmospheres or media such as solvents and cleaning agents, with a predominantly functional requirement for the surface.

 Core Range



Cylinder/valve combination DNCV, standard port pattern

Accessories

FESTO

Swivel flange SNCS

Material:
Die-cast aluminium





Dimensions and ordering data

For Ø	CN	EP	EX	FL	LT	MS	XC	Weight	Part No.	Type
[mm]	Ø H7	+0.2		±0.2				[g]		
32	10	10.5	14	22	13	15	142.7	85	174 397	SNCS-32
40	12	12	16	25	16	17	160.6	125	174 398	SNCS-40
50	16	15	21	27	16	20	171	210	174 399	SNCS-50
63	16	15	21	32	21	22	191.5	280	174 400	SNCS-63

Swivel flange SNCL

Material:
Die-cast aluminium



Dimensions and ordering data

For Ø	CD	EW	FL	L	MR	XC	Weight	Part No.	Type
[mm]	Ø H9	h12	±0.2				[g]		
32	10	26	22	13	10	142.7	75	174 404	SNCL-32
40	12	28	25	16	12	160.6	100	174 405	SNCL-40
50	12	32	27	16	12	171	160	174 406	SNCL-50
63	16	40	32	21	16	191.5	250	174 407	SNCL-63

Cylinder/valve combination DNCV, standard port pattern

FESTO

Accessories


Trunnion flange ZNCF/CRZNG

Material:

ZNCF: High-alloy stainless steel

CRZNG: Electrolytically polished high-alloy stainless steel

Free of copper, PTFE and silicone



Dimensions and ordering data									
For Ø	C2	C3	TD Ø e9	TK	TL	TM	US	XH	XL
[mm]									
32	71	86	12	16	12	50	45	18	128.7
40	87	105	16	20	16	63	54	21	145.6
50	99	117	16	24	16	75	64	26	156
63	116	136	20	24	20	90	75	27	171.5

For Ø	Basic version				High corrosion protection			
	CRC ¹⁾	Weight [g]	Part No.	Type	CRC ¹⁾	Weight [g]	Part No.	Type
[mm]								
32	2	130	174 411	ZNCF-32	4	150	161 852	CRZNG-32
40	2	240	174 412	ZNCF-40	4	260	161 853	CRZNG-40
50	2	390	174 413	ZNCF-50	4	430	161 854	CRZNG-50
63	2	600	174 414	ZNCF-63	4	640	161 855	CRZNG-63

1) Corrosion resistance class 2 according to Festo standard 940 070

Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

Corrosion resistance class 4 according to Festo standard 940 070

Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required.

Cylinder/valve combination DNCV, standard port pattern

Accessories

FESTO

Trunnion support LN2G


Material:

Trunnion support:

Anodised aluminium

Plain bearing: Plastic

Free of copper, PTFE and silicone



Dimensions and ordering data

For Ø	CR	DA	FK	FN	FS	H1	HB	KE	NH	TH	UL
[mm]	Ø D11	Ø H13	Ø ±0.1				Ø H13			±0.2	
32	12	11	15	30	10.5	15	6.6	6.8	18	32	46
40, 50	16	15	18	36	12	18	9	9	21	36	55
63	20	18	20	40	13	20	11	11	23	42	65

For Ø	Basic version				Variant CT – Free of copper, PTFE and silicone			
	CRC ¹⁾	Weight [g]	Part No.	Type	CRC ¹⁾	Weight [g]	Part No.	Type
32	2	125	32 959	LN2G-32	2	125	183 463	LN2G-32-CT
40, 50	2	400	32 960	LN2G-40/50	2	400	183 464	LN2G-40/50-CT
63	2	480	32 961	LN2G-63/80	2	480	183 465	LN2G-63/80-CT

1) Corrosion resistance class 2 according to Festo standard 940 070



Components requiring moderate corrosion resistance. Externally visible parts with primarily decorative surface requirements which are in direct contact with a surrounding industrial atmosphere or media such as cooling or lubricating agents.

Trunnion support CRLN2G

Material:

High-alloy steel

Free of copper, PTFE and silicone



Dimensions and ordering data

For Ø	CR	FK	FN	FS	H1	HB	NH	TH	UL	CRC ¹⁾	Weight	Part No.	Type
[mm]	Ø D11	Ø ±0.1				Ø H13		±0.2			[g]		
32	12	15	30	10.5	15	6.6	18	32	46	4	200	161 874	CRLN2G-32
40, 50	16	18	36	12	18	9	21	36	55	4	330	161 875	CRLN2G-40/50
63	20	20	40	13	20	11	23	42	65	4	440	161 876	CRLN2G-63/80

1) Corrosion resistance class 4 according to Festo standard 940 070

Components requiring higher corrosion resistance. Parts used with aggressive media, e.g. food or chemical industry. These applications should be supported with special tests with the media if required.

Core Range



Cylinder/valve combination DNCV, standard port pattern

Accessories



Adapter kit DPNC

Material:
Flange: Wrought aluminium alloy
Threaded pins, hex nuts: Galvanised steel



 **Note**
The maximum overall stroke length may not be exceeded when combining cylinders and multi-position kits.

Dimensions and ordering data						
For Ø	F1	ZJ	Max. overall stroke length	Weight	Part No.	Type
[mm]			[mm]	[g]		
32	27	120.7	1000	85	174 418	DPNC-32
40	27	135.6	1000	115	174 419	DPNC-40
50	32	144	1000	210	174 420	DPNC-50
63	28	159.5	1000	360	174 421	DPNC-63

Connecting two cylinders with identical piston Ø as a 3 or 4-position cylinder

A 3 or 4-position cylinder consists of two separate cylinders whose piston rods advance in opposing directions.


Depending upon actuation and stroke pattern, this type of cylinder can assume up to four positions. In each

case the cylinder is driven precisely against a stop. If one end of the piston rod is fixed, the cylinder barrel

executes the movement. The cylinder must be connected with flexible line connections.


Implementing 3 positions

Two cylinders with identical stroke length must be connected to this end.



Implementing 4 positions






Two cylinders with different stroke lengths must be connected to this end.




Cylinder/valve combination DNCV, standard port pattern

Accessories

FESTO

Ordering data – Mounting attachments				Technical data → 1 / 10.1-2			
Designation	For Ø	Part No.	Type	Designation	For Ø	Part No.	Type
Clevis foot LNG				Clevis foot LSN			
	32	33 890	LNG-32		32	5 561	LSN-32
	40	33 891	LNG-40		40	5 562	LSN-40
	50	33 892	LNG-50		50	5 563	LSN-50
	63	33 893	LNG-63		63	5 564	LSN-63
Clevis foot LSNG				Clevis foot LSNSG			
	32	31 740	LSNG-32		32	31 747	LSNSG-32
	40	31 741	LSNG-40		40	31 748	LSNSG-40
	50	31 742	LSNG-50		50	31 749	LSNSG-50
	63	31 743	LSNG-63		63	31 750	LSNSG-63
Clevis foot LBG				Clevis foot, lateral LQG			
	32	31 761	LBG-32		32	31 768	LQG-32
	40	31 762	LBG-40		40	31 769	LQG-40
	50	31 763	LBG-50		50	31 770	LQG-50
	63	31 764	LBG-63		63	31 771	LQG-63



Ordering data – Corrosion resistant mounting attachments				Technical data → 1 / 10.1-2			
Designation	For Ø	Part No.	Type	Designation	For Ø	Part No.	Type
Clevis foot CRLNG							
	32	161 840	CRLNG-32				
	40	161 841	CRLNG-40				
	50	161 842	CRLNG-50				
	63	161 843	CRLNG-63				

 Core Range

Cylinder/valve combination DNCV, standard port pattern

FESTO

Accessories

Ordering data – Piston rod attachments				Technical data → 1 / 10.3-2			
Designation	For Ø	Part No.	Type	Designation	For Ø	Part No.	Type
Rod eye SGS				Rod clevis SGA			
	32	9 261	SGS-M10x1,25		32	32 954	SGA-M10x1,25
	40	9 262	SGS-M12x1,25		40	10 767	SGA-M12x1,25
	50	9 263	SGS-M16x1,5		50	10 768	SGA-M16x1,5
	63				63		
Rod clevis SG				Self-aligning rod coupler FK			
	32	6 144	SG-M10x1,25		32	6 140	FK-M10x1,25
	40	6 145	SG-M12x1,25		40	6 141	FK-M12x1,25
	50	6 146	SG-M16x1,5		50	6 142	FK-M16x1,5
	63				63		
Coupling piece KSG				Coupling piece KSZ			
	32	32 963	KSG-M10x1,25		32	36 125	KSZ-M10x1,25
	40	32 964	KSG-M12x1,25		40	36 126	KSZ-M12x1,25
	50	32 965	KSG-M16x1,5		50	36 127	KSZ-M16x1,5
	63				63		
Adapter AD							
	32	157 333	AD-M10x1,25-1/8				
		157 334	AD-M10x1,25-1/4				
	40	160 256	AD-M12x1,25-1/4				
		160 257	AD-M12x1,25-3/8				


Ordering data – Corrosion resistant piston rod attachments				Technical data → 1 / 10.3-2			
Designation	For Ø	Part No.	Type	Designation	For Ø	Part No.	Type
Rod eye CRS GS				Rod clevis CRS G			
	32	195 582	CRSGS-M10x1,25		32	13 569	CRSG-M10x1,25
	40	195 583	CRSGS-M12x1,25		40	13 570	CRSG-M12x1,25
	50	195 584	CRSGS-M16x1,5		50	13 571	CRSG-M16x1,5
	63				63		


 Core Range

Cylinder/valve combination DNCV, standard port pattern

Accessories

FESTO

Ordering data – Guide units for variable strokes					Technical data → 1 / 10.4-2	
	For Ø [mm]	Stroke [mm]	With recirculating ball bearing guide		With plain-bearing guide	
			Part No.	Type	Part No.	Type
	32	10 ... 500	34 487	FENG-32-...-KF	34 481	FENG-32-...
	40	10 ... 500	34 488	FENG-40-...-KF	34 482	FENG-40-...
	50	10 ... 500	34 489	FENG-50-...-KF	34 483	FENG-50-...
	63	10 ... 500	34 490	FENG-63-...-KF	34 484	FENG-63-...

Ordering data – Guide units for fixed strokes (recirculating ball bearing guide only)					Technical data → 1 / 10.4-2	
	Stroke [mm]	Part No.	Type		Stroke [mm]	Part No. Type
	For Ø 32 mm				For Ø 40 mm	
	10 ... 50	34 493	FENG-32-50-KF		10 ... 50	34 499 FENG-40-50-KF
	10 ... 100	34 494	FENG-32-100-KF		10 ... 100	34 500 FENG-40-100-KF
	10 ... 160	34 495	FENG-32-160-KF		10 ... 160	34 501 FENG-40-160-KF
	10 ... 200	34 496	FENG-32-200-KF		10 ... 200	34 502 FENG-40-200-KF
	10 ... 250	150 289	FENG-32-250-KF		10 ... 250	34 503 FENG-40-250-KF
	10 ... 320	34 497	FENG-32-320-KF		10 ... 320	34 504 FENG-40-320-KF
	10 ... 400	150 290	FENG-32-400-KF		10 ... 400	150 291 FENG-40-400-KF
	10 ... 500	34 498	FENG-32-500-KF		10 ... 500	34 505 FENG-40-500-KF
	For Ø 50 mm				For Ø 63 mm	
	10 ... 50	34 506	FENG-50-50-KF		10 ... 50	34 513 FENG-63-50-KF
	10 ... 100	34 507	FENG-50-100-KF		10 ... 100	34 514 FENG-63-100-KF
	10 ... 160	34 508	FENG-50-160-KF		10 ... 160	34 515 FENG-63-160-KF
	10 ... 200	34 509	FENG-50-200-KF		10 ... 200	34 516 FENG-63-200-KF
	10 ... 250	34 510	FENG-50-250-KF		10 ... 250	34 517 FENG-63-250-KF
	10 ... 320	34 511	FENG-50-320-KF		10 ... 320	34 518 FENG-63-320-KF
	10 ... 400	150 292	FENG-50-400-KF		10 ... 400	34 519 FENG-63-400-KF
	10 ... 500	34 512	FENG-50-500-KF		10 ... 500	34 520 FENG-63-500-KF

 Core Range