

Soft-start/quick exhaust valves MS-SV, MS series, NPT

FESTO



Type codes

001	Series	
MS	MS series	
002	Size	
6	Grid dimension 62 mm	
003	Thread type	
N	NPT thread	
004	Function	
SV	Soft-start/quick exhaust valve	
005	Pneumatic connection, inch	
1/2	Female thread NPT 1/2	
AQN	Sub-base NPT1/4	
AQP	Sub-base NPT3/8	
AQR	Sub-base NPT1/2	
AQS	Sub-base NPT3/4	
006	Performance Level	
C	Category 1, 1-channel to ISO 13849-1	
E	Category 4, 2-channel with self-monitoring to ISO 13849-1	
007	Supply voltage	
10V24	24 V DC, 10 bar, connection pattern to EN 175301	
10V24C	24 V DC, 10 bar (connection pattern to EN 175301) without manual override	
10V24D	24V DC, 10 bar, M12 (connection pattern according to IEC 61076-2-101) without manual override	
10V24E	24 V DC, 10 bar, M12 (connection pattern according to IEC 61076-2-101) without manual override on the pilot actuator. With detenting internal manual override (can only be reset via 24 V)	
10V24F	24 V DC, 10 bar, M12 (connection pattern to IEC 61076-2-101). Non-detenting manual override on the pilot actuator	
10V24P	24 V DC, 10 bar, M12 (connection pattern to IEC 61076-2-101)	
ASIS	22 V - 31.6 V DC, AS-i Safety at Work, SPEC3.0 Profile 7.5.5	
008	Silencer	
	None	
S	Silencer	
SO	Open silencer	

009	Pressure gauge alternatives	
	None	
A4	Adapter for EN pressure gauge 1/4, without pressure gauge	
A8	Adapter for EN pressure gauge 1/8, without pressure gauge	
AD7	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/O	
AD8	Pressure sensor with switching display, M8 plug, threshold value comparator, PNP, N/C	
AD9	Pressure sensor with switching display, M8 plug, window comparator, PNP, N/O	
AD10	Pressure sensor with operational status indicator, M8 plug, window comparator, PNP, N/C	
AD11	Pressure sensor with LCD display, M12 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA	
AD12	Pressure sensor with LCD display, M8 plug, 4-pin, IO-Link®, PNP, NPN, 0...10 V, 1...5 V, 4...20 mA	
AG	MS pressure gauge	
RG	Integrated pressure gauge, red/green scale	

010	Alternative pressure gauge scale	
	MS pressure gauge	
PSI	psi	
MPA	MPa	

011	Multi-pin plug socket	
	None	
MP1	Multi-pin plug socket, Sub-D, 9-pin, screw terminal, without cable, static enable signals (EN1 = 24 V, EN2 = 24 V)	
MP3	Multi-pin plug socket, Sub-D, 9-pin, screw terminal, without cable, static enable signals (EN1 = 0 V, EN2 = 24 V), cross-circuit detection possible	

012	Type of mounting	
	Without mounting bracket	
WP	Mounting bracket basic design	
WPB	Mounting bracket for large wall gap	
WPM	Mounting bracket for hooking in service unit components	
WB	Mounting centrally at rear (wall mounting top and bottom), connecting plates not required	


013	Tamper protection	
	None	
MK	Full	

014	UL certification	
	None	
UL1	cULus ordinary location for Canada and USA	

015	EU certification	
	None	
EX2	II 3GD	

016	Flow direction	
	Flow direction from left to right	
Z	Flow direction from right to left	

Peripherals overview MS6N-SV-C



Mounting attachments and accessories

			Single device		Combination		→ Page/ Internet
			Without connecting plate	With connecting plate	Without connecting plate	With connecting plate	
[1]	MS6N-SV-C	Soft-start/quick exhaust valve	■	■	■	■	5
[2]	MS6-MV	Module connector	–	■	■	■	ms6-mv
[3]	MS6-WP, MS6-WPB, MS6-WPE, MS6-WPM	Mounting bracket	■	■	■	■	ms6-wp
[4]	MS6-WB	Mounting bracket	■	■	–	–	ms6-wb
[5]	MS6-SV-C-MK	Covering	■	■	■	■	25
[6]	MS6-END	Cover cap	–	–	■	–	ms6-end
[7]	MS6-AEND	Mounting plate	■ ¹⁾	–	■ ¹⁾	–	ms6-aend
[8]	MS6-AG...	Connecting plate SET	–	■ ¹⁾	–	■ ¹⁾	ms6-ag
	MS6-AQ...	Connecting plate SET	–	■ ¹⁾	–	■ ¹⁾	ms6-aq
[9]	AD11 ... AD12	Pressure sensor SPAU with LCD display	■	■	■	■	10
[10]	NEBA-M8...-LE4/NEBA-M12...-LE4	Connecting cable	■	■	■	■	27
[11]	AD7 ... AD10	Pressure sensor SDE5 with switching status indicator	■	■	■	■	10
[12]	NEBA-M8...-LE3	Connecting cable	■	■	■	■	27
[13]	A4	Adapter for EN pressure gauge 1/4	■	■	■	■	10
[14]	MA	Pressure gauge	■	■	■	■	27
[15]	AG, RG	MS pressure gauge	■	■	■	■	10
[16]	U-3/4-B	Silencer	■	■	■	■	26


1) Module connector MS6-MV [2] or mounting bracket MS6-WP, MS6-WPB, MS6-WPE, MS6-WPM [3] is required for mounting.

Peripherals overview MS6N-SV-C

Soft-start/quick exhaust valve MS6N-SV-C

Supply voltage
Code: 10V24, 10V24C

Supply voltage
Code: 10V24D, 10V24F, 10V24P



 **Note**

Additional accessories:

- Module connector for combination with size MS4/MS6 or size MS9
→ Internet: amv rmv
- Adapter for mounting on profiles
→ Internet: ipm


Mounting attachments and accessories

			Single device		Combination		→ Page/ Internet
			Without connecting plate	With connecting plate	Without connecting plate	With connecting plate	
[1]	MEB-LD	Illuminating seal	■	■	■	■	26
[2]	KMEB	Plug socket with cable	■	■	■	■	26
[3]	MSSD-EB	Plug socket	■	■	■	■	26
[4]	NEBA-M12G5	Connecting cable	■	■	■	■	27
[5]	NEBA-M12W5	Connecting cable	■	■	■	■	27


1) Module connector MS6-MV [5] or mounting bracket MS6-WP, MS6-WPB, MS6-WPE, MS6-WPM [6] is required for mounting.

Datasheet MS6N-SV-C


MS6N-SV-...-10V24, -10V24F, -10V24P



- - Flow rate
5700 l/min
- - Temperature range
0 ... +60°C
- - Operating pressure
3 ... 10 bar
- - www.festo.com



MS6N-SV-...-10V24C, -10V24D



Electropneumatic soft-start/quick exhaust valve for gradual pressurisation and quick exhausting of system components (single channel).
The main restrictor in the end cap permits a slower build-up of output pressure p2. Once the output pressure p2 has reached the set pressure switchover point (switching pressure), the valve opens and the full operating pressure p1 is available at the output.

- Suitable for applications with a high flow rate in restricted space with medium safety requirements up to controller category 1, Performance Level c
- High volumetric flow rate for pressurisation and exhausting
- The filling flow rate can be set for gradual pressure build-up with a restrictor
- Adjustable pressure switchover point
- Optional pressure sensor
- Optional covering for the control sections as tamper protection

Safety characteristics

Conforms to standard	EN ISO 13849-1
Safety function	Exhaust
	Avoidance of unexpected start-up (pressurisation)
Performance Level (PL)	Exhausting: up to category 1, PL c
	Prevention of unexpected start-up (pressurisation): up to category 1, PL c
Note on forced checking procedure	Switching frequency min. once a month
CE mark (see declaration of conformity) ¹⁾	To EU Machinery Directive
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6

¹⁾ Additional information: www.festo.com/catalogue/... → Support/Downloads.

Note The mechanical system is not tested in the controlled (i.e. pressurised) state.	Forced switch on/off: switching frequency should be at least once a month.	If the process-related switching frequency (safe exhausting) is less than once a month,	the machine's operator must carry out a forced switch off.
--	---	--	---

Datasheet MS6N-SV-C

General technical data		
Pneumatic connection 1, 2		
	Female thread	1/2 NPT
	Connecting plate AQ...	1/4 NPT, 3/8 NPT, 1/2 NPT or 3/4 NPT
Pneumatic connection 3		
3/4 NPT		
Actuation type		
Electrical		
Design		
Piston spool		
Type of mounting		
With accessories		
In-line installation		
Mounting position		
Any		
Pressure indicator		
Via pressure sensor for displaying the output pressure on LCD display and electrical output		
Via pressure sensor for displaying the output pressure by switching status indicator and electrical output		
Via pressure gauge for displaying the output pressure		
Via pressure gauge with red/green scale for displaying the output pressure		
Prepared for G1/4		
Valve function		
3/2-way valve, closed, monostable		
Soft-start function, adjustable		
Non-overlapping		
Yes		
Exhaust function		
Cannot be throttled		
Manual override 10V2 4, 10V24F		
At the pilot solenoid valve: non-detenting		
At the soft-start/quick exhaust valve: detenting, self-resetting		
10V24P		
At the pilot solenoid valve: non-detenting/detenting		
At the soft-start/quick exhaust valve: detenting, self-resetting		
10V24C, 10V24D		
None		
Reset method		
Mechanical spring		
Type of control		
Piloted		
Pilot air supply		
Internal		
Sealing principle		
Soft		

Characteristic flow rate values		
Pneumatic connection		
Female thread 1/2 NPT		
Standard nominal flow rate $q_{nN}^{1)}$ [l/min]		
in main flow direction 1 > 2		
5700		
Standard flow rate q_N [l/min], $p_2 = 6$ bar		
in exhaust direction 2 > 3		
7600 ²⁾		
C value [l/s*min]		
in main flow direction 1 > 2		
23.2		
b value		
in main flow direction 1 > 2		
0.4		

1) Measured at $p_1 = 6$ bar and $p_2 = 5$ bar, $\Delta p = 1$ bar

2) Measured with reference to atmosphere with silencer S.

Electrical data		
Characteristic coil data	10V24, 10V24P	24 V DC: 1.8 W; permissible voltage fluctuations $-10\%/+10\%$
	10V24C, 10V24D, 10V24F	24 V DC: 1.8 W; permissible voltage fluctuations $-15\%/+10\%$
Electrical connection	10V24, 10V24C	Plug, 2-pin, to EN 175301-803, type C
	10V24D, 10V24F, 10V24P	M12x1 to ISO 20401 in line with EN 61076-2-101
Degree of protection		
IP65 with plug socket		
Duty cycle [%]		
100		
Switching time off [ms]		
65		
Switching time on [ms]		
370		

Datasheet MS6N-SV-C

Operating and environmental conditions	
Operating pressure [bar]	3 ... 10
Operating medium	Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/ pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
Ambient temperature [°C]	0 ... +60 (0 ... +50) ¹⁾
Temperature of medium [°C]	0 ... +60 (0 ... +50) ¹⁾
Storage temperature [°C]	-10 ... +60 (0 ... +50) ¹⁾
Corrosion resistance class CRC ²⁾	2
CE marking (see declaration of conformity) ³⁾	To EU EMC Directive
	To EU Machinery Directive
	To EU Low Voltage Directive
	To EU RoHS Directive
UKCA marking (see declaration of conformity) ³⁾	To UK instructions for EMC
	To UK instructions for machines
	To UK RoHS instructions
Suitability for the food industry ³⁾	See supplementary material information (except for solenoid valve)


1) With pressure sensor AD...

2) Additional information: www.festo.com/x/topic/kbk3) Additional information: www.festo.com/catalogue/ms-sv → Support/Downloads.

Weights [g]	
Soft-start/quick exhaust valve	886
Soft-start/quick exhaust valve with silencer S	1006

Materials	
Housing	Die-cast aluminium
Piston rod	High-alloy stainless steel
Seals	NBR
Note on materials	RoHS-compliant
PWIS conformity	VDMA24364-B2-L

Adjusting elements



[1] Screw for adjusting the pressure switchover point

[2] Flow control screw for adjusting the filling time

[3] Manual override at the soft-start/quick exhaust valve:

- detenting, self-resetting as soon as the solenoid coil or manual override on the pilot solenoid valve is actuated (with 10V24, 10V24E, 10V24F, 10V24P)
- none (with 10V24C, 10V24D)

[4] Manual override at the pilot solenoid valve:

- non-detenting, actuation from above (with 10V24/10V24F)
- non-detenting/detenting, actuation from above (with 10V24P)
- none (with 10V24C, 10V24D, 10V24E)

Datasheet MS6N-SV-C

Dimensions – Basic version

Download CAD data → www.festo.com

With female thread 1/2, with cover plate

Supply voltage
10V24, 10V24C

Supply voltage
10V24D, 10V24F, 10V24P

1 = not assigned

2 = not assigned

3 = com (-)

4 = signal (+) solenoid 14

[1] Plug connection to
EN 175301-803

[2] Electrical connection M12x1 to
ISO 20401 in line with
EN 61076-2-101, 4-pin version
for connecting cable NEBA-M12

→ Flow direction

With silencer S

Type	B1	B4	B5	D1	D2	D5	L1	L2	L4
MS6N-SV-C	62	31	76	1/2 NPT	M12x1	3/4 NPT	144	71	135

Type	L8		L9	
	10V24, 10V24C	10V24D, 10V24F, 10V24P	10V2 4, 10V24C	10V24D, 10V24F, 10V24P
MS6N-SV-C	33	37	24	26

Dimensions – Pressure gauge/pressure gauge alternatives

Download CAD data → www.festo.com

Integrated MS pressure gauge with standard scale AG or red/green scale RG,
display unit [bar]

Adapter A4 for EN pressure gauge 1/4, without pressure gauge

[1] Plug connection to
EN 175301-803

[2] Electrical connection M12x1 to
ISO 20401 in line with
EN 61076-2-101, 4-pin version
for connecting cable NEBA-M12

→ Flow direction

With silencer S

Type	B4	B5	D4
MS6N-SV-...AG	31	77	–
MS6N-SV-...RG	31	78.5	–
MS6N-SV-...A4	31	78.5	G1/4

8

→ Internet: www.festo.com/catalogue/...

Subject to change – 2025/12


Datasheet MS6N-SV-C

Dimensions – Pressure sensor

Pressure sensor with switching status indicator AD7 ... AD10

Download CAD data → www.festo.com

Datasheets → Internet: sde5



[AD7]:

SDE5-D10-O-...-P-M8 with 3-pin plug M8x1, threshold value comparator, 1 switching output PNP, N/O contact

[AD9]:

SDE5-D10-O3-...-P-M8 with 3-pin plug M8x1, window comparator, 1 switching output PNP, N/O contact

[AD8]:


SDE5-D10-C-...-P-M8 with 3-pin plug M8x1, threshold value comparator, 1 switching output PNP, N/C contact

[AD10]:

SDE5-D10-C3-...-P-M8 with 3-pin M8x1 plug, window comparator, 1 switching output PNP, N/C contact

Pressure sensor with LCD display AD11 ... AD12

Datasheets → Internet: spau



[AD11]:

SPAU-P10R-MS...-L-PNLK-M12D with 4-pin plug M12x1 A-coded, switching output 2x PNP or 2x NPN switchable and 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA analogue

[AD12]:

SPAU-P10R-MS...-L-PNLK-M8D with 4-pin plug M8x1 A-coded, switching output 2x PNP or 2x NPN switchable and 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA analogue

Type	B2	B3	B4	B5	B6	D6	L5	L6
MS6-SV-...-AD7, AD8, AD9, AD10	31	79.1	–	51	16	M8x1	–	–
MS6-SV-...-AD11	31	101.8	93.7	51	32	M12x1	41.2	39
MS6-SV-...-AD12						M8x1	37.9	

Ordering data – Modular product system MS6N-SV-C

Ordering table		Conditions	Code	Enter code
Grid dimension	[mm] 62			
Module no.	548714			
Series	Standard		MS	MS
Size	6		6	6
Thread type	NPT thread		N	N
Function	Soft-start/quick exhaust valve		-SV	-SV
Pneumatic connection	Female thread 1/2 NPT		-1/2	
	Connecting plate 1/4 NPT		-AQN	
	Connecting plate 3/8 NPT		-AQP	
	Connecting plate 1/2 NPT		-AQR	
	Connecting plate 3/4 NPT		-AQS	
Performance Level	Category 1, single-channel, to EN ISO 13849-1		-C	-C
Supply voltage	24 V DC (connection pattern to EN 175301), 3 ... 10 bar, Manual override • At the soft-start/quick exhaust valve: detenting, self-resetting • At the pilot solenoid valve: non-detenting		-10V24	
	24 V DC (connection pattern to EN 175301), 3 ... 10 bar, No manual override		-10V24C	
	24 V DC, M12x1 to ISO 20401 in line with EN 61076-2-101, 3 ... 10 bar, No manual override		-10V24D	
	24 V DC, M12x1 to ISO 20401 in line with EN 61076-2-101, 3 ... 10 bar, Manual override • At the soft-start/quick exhaust valve: detenting, self-resetting • At the pilot solenoid valve: non-detenting		-10V24F	
	24 V DC, M12x1 to ISO 20401 in line with EN 61076-2-101, 3 ... 10 bar, Manual override • At the soft-start/quick exhaust valve: detenting, self-resetting • At the pilot solenoid valve: non-detenting/detenting		-10V24P	

Ordering data – Modular product system MS6N-SV-C

Ordering table		Grid dimension	[mm]	62	Conditions	Code	Enter code
Silencers	Silencers					-S	
Pressure gauge/pressure gauge alternatives	MS pressure gauge	[1]				-AG	
	Adapter for EN pressure gauge 1/4, without pressure gauge					-A4	
	Integrated pressure gauge, red/green scale	[1]				-RG	
	Pressure sensor SDE5 with switching status indicator, plug M8, threshold value comparator, PNP, N/O	[2]				-AD7	
	Pressure sensor SDE5 with switching status indicator, plug M8, threshold value comparator, PNP, N/C	[2]				-AD8	
	Pressure sensor SDE5 with switching status indicator, plug M8, window comparator, PNP, N/O	[2]				-AD9	
	Pressure sensor SDE5 with switching status indicator, plug M8, window comparator, PNP, N/C	[2]				-AD10	
	Pressure sensor SPAU with LCD display, M12 plug 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA	[2]				-AD11	
	Pressure sensor SPAU with LCD display, M8 plug 4-pin, IO-Link®, PNP, NPN, 0 ... 10 V, 1 ... 5 V, 4 ... 20 mA	[2]				-AD12	
Alternative pressure gauge scale	bar	[3]				-BAR	
	MPa	[3]				-MPA	
Type of mounting	Mounting bracket standard design					-WP	
	Mounting bracket for attaching service unit components	[4]				-WPM	
	Mounting bracket for large wall gap					-WPB	
	Mounting bracket centrally at rear (wall mounting top and bottom), connecting plates not required					-WB	
Tamper protection	Complete (manual override at soft-start/quick exhaust valve blocked, setting screws blocked, manual override at pilot solenoid valve blocked)					-MK	
Flow direction	Flow direction from right to left					-Z	


[1] **AG, RG** Pressure gauge scale in psi. With pressure gauge RG: PSI scale only as auxiliary scale (inner scale), outer scale in bar

[2] **AD7 ... AD12** Measuring range max. 10 bar

[3] **BAR, MPA** Only in combination with pressure gauge AG or RG

[4] **WPM** Only with connecting plate AQN, AQP, AQR or AQS

Peripherals overview MS6N-SV-E



Note

Additional accessories:

- Module connector for combination with size MS4/MS6 or size MS9
→ Internet: amv rmv
- Adapter for mounting on profiles
→ Internet: ipm


Peripherals overview MS6N-SV-E

Mounting attachments and accessories			Single device		Combination		→ Page/ Internet
			Without connecting plate	With connecting plate	Without connecting plate	With connecting plate	
[1]	MS6-SV-E	Soft-start/quick exhaust valve	■	■	■	■	14
[2]	MS6-MV	Module connector	–	–	■	■	ms6-mv
[3]	MS6-WPB	Mounting bracket	■	■	■	■	ms6-wpb
[4]	MS6-WPE	Mounting bracket	■	■	■	■	ms6-wpe
[5]	MS6-END	Cover cap	–	–	■	–	ms6-end
[6]	MS6-AEND	Mounting plate	■ ¹⁾	–	■ ¹⁾	–	ms6-aend
[7]	MS6-AG...	Connecting plate SET	–	■ ¹⁾	–	■ ¹⁾	ms6-ag
	MS6-AQ...	Connecting plate SET	–	■ ¹⁾	–	■ ¹⁾	ms6-aq
[8]	MA	Pressure gauge	■	■	■	■	27
[9]	A4	Adapter for EN pressure gauge 1/4	■	■	■	■	21
[10]	AG/RG	MS pressure gauge	■	■	■	■	21
[11]	AD	Adapter	■	■	■	■	26
[12]	UOS-1-LF	Silencer	■	■	■	■	24
[13]	UOS-1	Silencer	■	■	■	■	24
[14]	NECA	Multi-pin plug socket	■	■	■	■	22

1) Module connector MS6-MV [2] or mounting bracket MS6-WPB [3] or MS6-WPE [4] is required for assembly.

Datasheet MS6N-SV-E

Function



- Flow rate
4300 l/min
- Temperature range
-10 ... +50°C
- Operating pressure
3.5 ... 10 bar
- www.festo.com



The electropneumatic soft-start/quick exhaust valve is used to reduce pressure quickly and safely and to build up pressure gradually in industrial pneumatic piping systems and terminal equipment.

The device is a self-testing, redundant mechatronic system conforming to the requirements of EN ISO 13849-1. The safety-related pneumatic protection

objective of safe exhausting is also guaranteed in the event of faults inside the valve (e.g. due to wear, contamination, electronic faults). The 2-channel design and its monitoring enables the device to meet controller category 3 and 4 requirements. This enables a Performance Level of max. "e".

The device receives the secure enable signals (EN1/EN2) via the electrical

connection (multi-pin plug socket NECA Sub-D, 9-pin or AS-i connecting cable). These signals are generated commercially available electronic or electromechanical safety switching devices which monitor the protective equipment of the machine (e.g. emergency stop, light curtain, electrical door switch of a protective enclosure, etc.).

- Performance Level "e"/Category 4 to EN ISO 13849-1
- Conforms to standard IEC 61508
- Switching time delay adjustable via a restrictor for gradual pressure build-up
- Optional pressure sensor

- **Note**

The MS6N-SV-...-E-10V24 should only be used in combination with the multi-pin plug socket NECA approved for it. The multi-pin plug socket can be ordered via the modular product system (MP... → 21) or as an accessory (NECA → 22).

- **Note**

To avoid back pressures, it is recommended that the device be operated together with the silencer UOS-1. The silencer can be ordered via the modular product system (SO → 21) or as an accessory (UOS-1 → 24).

- **Note**

Only devices that do not impair the pneumatic protective measure – safe exhausting – may be placed downstream of the MS6-SV-...-E. The MS6-SV-...-D is not approved for use as a press safety valve.

Safety characteristics	
Type	MS6N-SV-...-E-10V24
Conforms to standard	EN ISO 13849-1
Safety function	Exhaust
	Avoidance of unexpected start-up (pressurisation)
Performance Level (PL)	Exhaust: up to category 4, PL e
	Prevention of unexpected start-up (pressurisation): up to category 4, PL e
Safety integrity level (SIL)	Exhaust: SIL 3
	Avoidance of unexpected start-up (pressurisation): SIL 3
Note on forced checking procedure	Switching frequency min. once a month
Certificate issuing authority ¹⁾	IFA 1001180
Shock resistance	Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance	Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6

- **Note**

The mechanical system is not tested in the controlled (i.e. pressurised) state.




Forced switch on/off: switching frequency should be at least once a month.

If the process-related switching frequency (safe exhausting) is less than once a month,

the machine's operator must carry out a forced switch off.

Datasheet MS6N-SV-E

Operational principle of the multi-pin plug socket NECA				
Enable signal status		Status MS6N-SV-...-E-10V24 with multi-pin plug socket		
EN1	EN2	NECA-...-MP1	NECA-...-MP3	NECA-...-MP5
0 V	0 V	Unpressurised	MS6N-SV-...-E-10V24 switches to fault mode.	MS6N-SV-...-E-10V24 does not switch to fault mode, but remains in the safe, unpressurised state. Note: Detection of cross-circuits and error detection/evaluation necessary via external controller.
0 V	24 V	MS6N-SV-...-E-10V24 switches to fault mode.	Pressurised	Pressurised
24 V	24 V	Pressurised	MS6N-SV-...-E-10V24 switches to fault mode.	MS6N-SV-...-E-10V24 does not switch to fault mode, but remains in the safe, unpressurised state. Note: Detection of cross-circuits and error detection/evaluation necessary via external controller.
24 V	0 V	MS6N-SV-...-E-10V24 switches to fault mode.	Unpressurised	Unpressurised

MS6-SV-E-10V24 with multi-pin plug socket NECA	
NECA-...-MP1	
	
	• Static enable signals (EN1 = 24 V, EN2 = 24 V).
	• Cycle end enable signals (EN1 = 0 ... 24 V, EN2 = 0 ... 24 V) for detecting cross-circuits. Detection of cross-circuits by clock signals is always carried out by the safety relay unit/safety PLC.  Note Since the clock outputs from different controller manufacturers are not standardised, their usability must be checked in each case. If the clock pulse is outside the specified limits, the MS6N-SV-...-E-10V24 detects is as an error and a safe shutdown is initiated.

Datasheet MS6N-SV-E

MS6-SV-E-10V24 with multi-pin plug socket NECA		
NECA-...-MP3		
		 Note The multi-pin plug socket NE-CA-S1G9-P9-MP3 is intended for conventional circuitry with electromechanical safety relays. If problems arise when used with bipolar semiconductor outputs, use the multi-pin plug socket NECA-S1G9-P9-MP5.
		• Static enable signals with opposite potentials. • Time delay of the level change of the enable signals is monitored. • Behaviour on detection of a cross-circuit: – MS6N-SV-...-E-10V24 in exhausted state: remains in safe state and goes into error mode. – MS6N-SV-...-E-10V24 in pressurised state: goes into safe state and goes into error mode.
NECA-...-MP5		
		 Note A cross-circuit between the enable signals EN1/EN2 is not detected and does not cause an error response. The system is pressurised only if the enable signals are applied correctly.
		• Static enable signals with opposite potentials. • Time delay of the level change of the enable signals is not monitored. • Behaviour on detection of a cross-circuit (by upstream safety relay unit/PLC): – MS6N-SV-...-E-10V24 in exhausted state: remains in safe state and does not go into error mode. – MS6N-SV-...-E-10V24 in pressurised state: goes into safe state and does not go into error mode. • Enable signals are galvanically separated from the supply voltage.

Datasheet MS6N-SV-E

General technical data		
Pneumatic connection 1, 2		
	Female thread	1/2 NPT
	Connecting plate AQ...	1/4 NPT, 3/8 NPT, 1/2 NPT or 3/4 NPT
Pneumatic connection 3		
1 NPT		
Actuation type		
Electrical		
Design		
Piston seat		
Type of mounting		
With accessories		
In-line installation		
Mounting position		
Any		
Pressure indicator		
Via pressure sensor for displaying the output pressure on LCD display and electrical output		
Via pressure gauge for displaying the output pressure		
Via pressure gauge with red/green scale for displaying the output pressure		
Prepared for G1/4		
Position sensing principle		
Magnetic piston principle		
Valve function		
3/2-way valve, closed, monostable		
Soft-start function, adjustable		
Non-overlapping		
No		
Exhaust function		
Cannot be throttled		
Manual override		
None		
Reset method		
Mechanical spring		
Type of control		
Piloted		
Pilot air supply		
Internal		
Sealing principle		
Soft		

Characteristic flow rate values		
Pneumatic connection		
Female thread 1/2 NPT		
Standard nominal flow rate $q_{nN}^{(1)}$ [l/min]		
in main flow direction 1 → 2		
4300		
Standard flow rate q_N [l/min], $p_2 = 6$ bar		
in exhaust direction 2 → 3		
9000 ⁽²⁾		
C value [l/s*min]		
in main flow direction 1 → 2		
19.3		
b value		
in main flow direction 1 → 2		
0.21		

1) Measured at $p_1 = 6$ bar and $p_2 = 5$ bar, $\Delta p = 1$ bar

2) Measured with reference to atmosphere with silencer UOS-1.

Electrical data		
Electrical connection		
Sub-D 9-pin		
Nominal operating voltage [V DC]		
24		
Permissible voltage fluctuations [%]		
±10		
Operating voltage range for AS-interface [V DC]		
–		
Duty cycle [%]		
100		
Max. switching frequency [Hz]		
0.5		
Switching time off [ms]		
40		
Switching time on [ms]		
130		
Signal status indication		
LED and floating contact		
Degree of protection		
IP65 with plug socket		

Datasheet MS6N-SV-E

Operating and environmental conditions		
Operating pressure	[bar]	3.5 ... 10
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]
Note on the operating/ pilot medium		Lubricated operation possible (in which case lubricated operation will always be required)
Ambient temperature	[°C]	-10 ... +50 (0 ... +50) ¹⁾
Temperature of medium	[°C]	-10 ... +50 (0 ... +50) ¹⁾
Storage temperature	[°C]	-10 ... +50 (0 ... +50) ¹⁾
Corrosion resistance class CRC ²⁾		2
Noise level	[dB(A)]	75 (with silencer UOS-1)
CE mark (see declaration of conformity) ⁴⁾		To EU EMC Directive ³⁾
		To EU Machinery Directive
		To EU Low Voltage Directive
		To EU RoHS Directive
UKCA marking (see declaration of conformity) ⁴⁾		To UK instructions for EMC
		To UK instructions for machines
		To UK RoHS instructions
Certificate issuing authority ⁴⁾		IFA 1001180
		Intertek UK-MCR-0086
		TÜV 44 799 12 556236 000
UL certification ⁴⁾		c UL us - Recognized (OL)
Certification		RCM
KC mark		KC EMC

1) With pressure sensor AD...

2) Additional information: www.festo.com/x/topic/kbk3) For information about the area of use, see the EC declaration of conformity at: www.festo.com/catalogue/... → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.


4) Additional information: www.festo.com/catalogue/ms-sv → Support/Downloads.

Weights [g]	
Soft-start/quick exhaust valve	2000
Soft-start/quick exhaust valve with silencer UOS-1	2200

Materials	
Housing	Die-cast aluminium
Piston rod	High-alloy stainless steel
Seals	NBR
Note on materials	RoHS-compliant
PWIS conformity	VDMA24364-B2-L

Datasheet MS6N-SV-E

Switch-through point

Pressure p as a function of time t 

- [1] Tolerance range
- [2] Switch-through point
- [3] Filling time is adjustable by a restrictor

**Note**


The +20%/–10% switching point tolerance refers to the operating pressure p_1 .

Example: A switching point from 1.6 bar to 2.8 bar is permissible at an operating pressure of 4 bar.

Dimensions – Basic version

with supply voltage 10V24,

with female thread 1/2 NPT, with cover plate

Download CAD data → www.festo.com

- [1] Regulating screw for throttle valve
- [2] Silencer UOS-1
- [3] Multi-pin plug socket NECA
- [4] Dimension without cable
- [5] Adapter AD
- [6] M12 socket, 5-pin
- [7] M12 pin, 5-pin

→ Flow direction

Type	B1	B2	B3	B4	D1	D5	D6	L1	L2	L3	L4
MS6N-SV-1/2-E-10V24	62	59	104	23	1/2 NPT	1 NPT	55	228	81	61	174



Datasheet MS6N-SV-E

Dimensions – Pressure gauge/pressure gauge alternatives

integrated MS pressure gauge AG with standard scale AG or red/green scale RG

Download CAD data → www.festo.com

Adapter A4 for EN pressure gauge 1/4, without pressure gauge



→ Flow direction

→ Flow direction

Type	B2	B3	D4
MS6N-SV-...-E-...-AG	59	105	-
MS6N-SV-...-E-...-RG	59	106.5	-
MS6N-SV-...-E-...-A4	59	106.5	G1/4

Ordering data – Modular product system MS6N-SV-E

Ordering table		Conditions	Code	Enter code
Grid dimension	[mm] 62			
Module no.	548714			
Series	Standard		MS	MS
Size	6		6	6
Thread type	NPT thread		N	N
Function	Soft-start/quick exhaust valve		-SV	-SV
Pneumatic connection	Female thread 1/2 NPT		-1/2	
	Connecting plate 1/4 NPT		-AQN	
	Connecting plate 3/8 NPT		-AQP	
	Connecting plate 1/2 NPT		-AQR	
	Connecting plate 3/4 NPT		-AQS	
Performance Level	Category 4, 2-channel with self-monitoring to ISO 13849-1		-E	-E
Supply voltage	24 V DC		-10V24	
Silencers	Open silencer		-SO	
Pressure gauge/pressure gauge alternatives	MS pressure gauge	[1]	-AG	
	Adapter for EN pressure gauge 1/4, without pressure gauge		-A4	
	Integrated pressure gauge, red/green scale	[1]	-RG	
Alternative pressure gauge scale	bar	[2]	-BAR	
	MPa	[2]	-MPA	
Multi-pin plug socket	Sub-D, 9-pin, screw terminal, without cable, static enable signals (EN1 = 24 V, EN2 = 24 V)		-MP1	
	Sub-D, 9-pin, screw terminal, without cable, static enable signals (EN1 = 0 V, EN2 = 24 V), Detection of cross-circuit contacts possible		-MP3	
	Sub-D, 9-pin, screw terminal, without cable, static enable signals (EN1 = 0 V, EN2 = 24 V), galvanic isolation of enable signal from the supply voltage		-MP5	
Type of mounting	Mounting bracket for large mounting spacing		-WPB	
UL certification	cULus, ordinary location for Canada and USA		-UL1	
Flow direction	Flow direction from right to left		-Z	

[1] **AG, RG** Pressure gauge scale in psi. With pressure gauge RG: PSI scale only as auxiliary scale (inner scale), outer scale in bar.

[2] **BAR, MPA** Only in combination with pressure gauge AG or RG

Accessories

Multi-pin plug socket NECA

(order code in the modular product system: MP1/MP3/MP5)

- for soft-start/quick exhaust valve
MS6N-SV-E-10V24



Technical data		
Type of mounting		Via through-hole
Electrical connection 1		Socket, sub-D, 9-pin
Electrical connection 2		Screw terminal, 9-pin
Operating voltage range	[V DC]	21.6 ... 26.4
Nominal operating voltage	[V DC]	24
Acceptable current load at 40°C	[A]	1.0
Connection cross section	[mm ²]	0.34 ... 1.0 without wire end sleeves
	[mm ²]	0.34 ... 0.5 with wire end sleeves
Permissible cable diameter	[mm]	5.0 ... 10.0
Degree of protection to IEC 60529		IP65

Operating and environmental conditions		
Relative humidity		95%, non-condensing
Ambient temperature	[°C]	0 ... +50
Storage temperature	[°C]	-20 ... +70
Corrosion resistance class CRC ¹⁾		2


1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

Materials	
Housing	PA-reinforced
Screws	Steel
Union nut	Brass
Seals	NBR

Accessories

Dimensions

Download CAD data → www.festo.com

B1	H1	L1	L2
61	20	61	54.1

Ordering data

Description	Connection	Weight [g]	Part no.	Type
for MS6N-SV-E-10V24	Without cable, static enable signals (EN1 = 24 V, EN2 = 24 V)	60	548719	NECA-S1G9-P9-MP1
	Without cable, static enable signals (EN1 = 0 V, EN2 = 24 V), detection of cross-circuits possible	60	552703	NECA-S1G9-P9-MP3
	Without cable, static enable signals (EN1 = 0 V, EN2 = 24 V), galvanic isolation of enable signals from the supply voltage	60	573695	NECA-S1G9-P9-MP5

Accessories

Silencer UOS-1

(order code in the modular product system: SO)

- for soft-start/quick exhaust valve MS6N-SV-D/E

Silencer UOS-1-LF

- for soft-start/quick exhaust valve MS6N-SV-D/E



Note

The space-saving silencer UOS-1-LF may only be used for applications with low exhaust rates. Pneumatic connection 2 at the soft-start/quick exhaust valve MS6N-SV-D/E must be reduced to 1/4 NPT by a connecting plate MS6-AQN.



Technical data	
Pneumatic connection	G1
Design	Open silencer
Type of mounting	With male thread
Mounting position	Any
Type of seal on screwed trunnion	No seal
Noise level	75 dB(A)

Operating and environmental conditions		
Operating pressure	[MPa]	0 ... 1
	[bar]	0 ... 10
Operating medium	Compressed air to ISO 8573-1:2010 [–:–:–]	
Ambient temperature	[°C]	–10 ... +50
Corrosion resistance class CRC ¹⁾	2	


1) Additional information: www.festo.com/x/topic/kbk

Materials		
Type	UOS-1	UOS-1-LF
Housing	POM	Wrought aluminium alloy
Sleeve	Wrought aluminium alloy	–
Cushioning insert	PE	
Note on materials	RoHS-compliant	
PWIS conformity	VDMA24364-B1/B2-L	


Dimensions

Download CAD data → www.festo.com

UOS-1



UOS-1-LF



Type	D1	D2	L1	L2
		Ø		
UOS-1	G1	55	156.5	11.5
UOS-1-LF			72.2	13

Ordering data		Weight	Part no.	Type
Description		[g]		
for MS6N-SV-D/E	For high exhaust rate	200	552252	UOS-1
	For low exhaust rate	157.9	1901207	UOS-1-LF

Accessories

Covering MS-SV-MK

(Order code in the modular product system: MK)

- for soft-start/quick exhaust valve MS6N-SV-C

Note on materials: RoHS-compliant




MS6-SV-C-MK



Ordering data		CRC ¹⁾	Part no.	Type
Description				
for MS6N-SV-C	Tamper protection for manual override at the soft-start/quick exhaust valve, flow control screw, adjusting screw for pressure switchover point and manual override at the pilot solenoid valve	2	8001479	MS6-SV-C-MK


1) Corrosion resistance class CRC 2 to Festo standard FN 940070
Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.


Accessories

Ordering data – Adapter AD					
	Description	Pneumatic connection		Part no.	Type
		1	2		
	for MS6N-SV-E	1 NPT	G1	546547	AD-1NPT-G1-I

Ordering data – Silencer U-...-B						Datasheets → Internet: u
	Description	Pneumatic connection	Order code in the modular product system	Part no.	Type	
	for MS6N-SV-C	3/4 NPT	S	566823	U-3/4-B-NPT	


Ordering data – Proximity switch SMT								Datasheets → Internet: smt
	Description	Switching output	Switching element function	Electrical connection	Cable length [m]	Order code in the modular product system	Part no.	Type
	for MS6N-SV-D	PNP	N/O	Cable with plug M8x1, 3-pin	0.3	2M8/S3	574334	SMT-8M-A-PS-24V-E-0.3-M8
				Cable with plug M12x1, 3-pin	0.3	2M12/S3	574337	SMT-8M-A-PS-24V-E-0.3-M12
	for MS6N-SV-D	PNP	N/O	Cable, 3-wire	5	20E/S3	574336	SMT-8M-A-PS-24V-E-5.0-OE


Ordering data – Plug socket MSSD							Datasheets → Internet: mssd
	Description	Electrical connection	Cable fitting	Type of mounting	Part no.	Type	
	For MS6-SV-C/D	3-pin	Pg7	M2.5 central screw	151687	MSSD-EB	
		3-pin	M12	M2.5 central screw	539712	MSSD-EB-M12	

Ordering data – Plug socket with cable KMEB								Datasheets → Internet: kmeb
	Description	Operating voltage	Electrical connection	Switching status indication	Cable length [m]	Part no.	Type	
	for MS6N-SV-C/D	24 V DC	2-pin	LED	2.5	547268	KMEB-3-24-2.5-LED	
				–	5	547269	KMEB-3-24-5-LED	
			3-pin	LED	2.5	547270	KMEB-3-24-2.5	
				–	5	547271	KMEB-3-24-5	
		230 V AC	3-pin	–	2.5	151688	KMEB-1-24-2.5-LED	
					5	151689	KMEB-1-24-5-LED	
					10	193457	KMEB-1-24-10-LED	
					2.5	151690	KMEB-1-230AC-2.5	
					5	151691	KMEB-1-230AC-5	

Ordering data – Illuminating seal MEB-LD					Datasheets → Internet: meb	
	Description	Operating voltage range		Part no.	Type	
	For plug socket with cable KMEB and plug socket MSSD-EB	12 ... 24 V DC		151717	MEB-LD-12-24DC	
		230 V DC/AC ±10%		151718	MEB-LD-230AC	

Accessories

Ordering data – Connecting cable NEBA-M8						Datasheets → Internet: neba
	Electrical connection	Number of cores	Cable length [m]	Part no.	Type	
	M8x1, straight socket	3	2,5	8078223	NEBA-M8G3-U-2.5-N-LE3	
			5	8078224	NEBA-M8G3-U-5-N-LE3	
	M8x1, angled socket	3	2,5	8078230	NEBA-M8W3-U-2.5-N-LE3	
			5	8078231	NEBA-M8W3-U-5-N-LE3	

Ordering data – Connecting cable NEBA-M12						Datasheets → Internet: neba
	Electrical connection	Number of cores	Cable length [m]	Part no.	Type	
	M12x1, straight socket	4	2,5	8078239	NEBA-M12G5-U-2.5-N-LE4	
			5	8078240	NEBA-M12G5-U-5-N-LE4	
	M12x1, angled socket	4	2,5	8078248	NEBA-M12W5-U-2.5-N-LE4	
			5	8078249	NEBA-M12W5-U-5-N-LE4	

Ordering data – Pressure gauge MA						
	Nominal size	Pneumatic connection	Display range		Part no.	Type
			[bar]	[psi]		
	Pressure gauge MA, EN 837-1					Datasheets → Internet: ma
	40	R1/4	0 ... 16	0 ... 232	187080	MA-40-16-R1/4-EN
		G1/4	0 ... 16	0 ... 232	183901	MA-40-16-G1/4-EN
	Pressure gauge MA, EN 837-1, with red/green range					Datasheets → Internet: ma
	50	R1/4	0 ... 16	–	525729	MA-50-16-R1/4-E-RG