


Round cylinders DSNU

FESTO



Key features

At a glance

DSNU-8 ... 63

- Stainless steel piston rod
- Good running performance and long service life
- Piston rod with male and female thread

- Extensive range of accessories makes it possible to install the cylinder virtually anywhere

DSNU-8 ... 25



- The basic versions conform to ISO 6432, variants are based on these standards

Wide choice of variants

| DSNU | DSNU-...-MA | DSNU-...-MQ | DSNU-...-MH |
|---|---|---|---|
| <ul style="list-style-type: none"> • Piston Ø 8 ... 63 mm • Cylinder barrel made of stainless steel • Bearing and end caps made of wrought aluminium alloy | <ul style="list-style-type: none"> • Piston Ø 8 ... 63 mm • Cylinder barrel made of stainless steel • Bearing cap with threaded flange • Short end cap with axial supply port | <ul style="list-style-type: none"> • Piston Ø 8 ... 63 mm • Cylinder barrel made of stainless steel • Bearing cap with threaded flange • Short end cap with lateral supply port | <ul style="list-style-type: none"> • Piston Ø 8 ... 63 mm • Cylinder barrel made of stainless steel • Direct mounting on bearing cap • Short end cap with lateral supply port |



DSNU-...-KP

- Piston Ø 8 ... 63 mm
- Cylinder barrel made of stainless steel
- With clamping unit

DSNU-...-Q

- Piston Ø 12 ... 63 mm
- Cylinder barrel made of stainless steel
- With square piston rod

DSNU-...-KE






- Piston Ø 8 ... 63 mm
- Through piston rod with stroke adjustment
- Setting range of the advanced end position



Cushioning types

| | Cushioning P | Cushioning PPS | Cushioning PPV |
|-----------------------|--|---|--|
| Operating mode | <ul style="list-style-type: none"> • The drive is fitted with polymer elastic end-position cushioning | <ul style="list-style-type: none"> • The drive is fitted with self-adjusting end-position cushioning | <ul style="list-style-type: none"> • The drive is fitted with adjustable end-position cushioning |
| Application | <ul style="list-style-type: none"> • Small loads • Low speeds • Low impact energies | <ul style="list-style-type: none"> • Small to medium loads • Low to medium speeds • Medium impact energies | <ul style="list-style-type: none"> • Medium to large loads • High speeds • High impact energies |
| Advantages | <ul style="list-style-type: none"> • No adjustment required • Saves time | <ul style="list-style-type: none"> • No adjustment required • Saves time • Powerful | <ul style="list-style-type: none"> • Very powerful |

Key features

| Variants from the modular product system | | |
|---|---|--|
| Symbol | Key features | Description |
|  | S2 Through piston rod | For working at both ends with the same force in the forward and return stroke, for attaching external stops |
|  | KE Stroke adjustment, advancing | Through piston rod with adjustment component mounted on one side. For limiting the advancing end position and to set a precise position. |
|  | S6 Heat-resistant seals | Temperature resistance up to max. 120°C |
|  | S10 Constant motion at low piston speeds | Suitable for very slow and constant (slow speed) and stick-slip-free movements. With very low break-away pressure compared with the standard (low friction). |
|  | L Low friction | <ul style="list-style-type: none"> • Break-away pressure: low • Dynamic response: suitable for very fast movements, especially at low operating pressures Application example: very dynamic movements with no standstill |
|  | ...K2 Extended male piston rod thread | – |
|  | K3 Female piston rod thread | – |
|  | ...K5 – Special piston rod thread | Metric standard thread to ISO |
|  | ...K6 – Shortened male piston rod thread | – |
|  | ...K8 – Extended piston rod | – |
|  | R3 High corrosion protection | All external cylinder surfaces comply with corrosion resistance class CRC 3 to Festo standard 940070. The piston rod is made from corrosion- and acid-resistant steel |
|  | R8 Dust protection (wiper) (32 ... 63 mm) | The cylinder has a hard-chrome-plated piston rod and a hard wiper, which protects against dry, dusty media |
|  | A1 Wiper variant (12 ... 63 mm) | Increased chemical resistance: For longer service life, e.g. when using cooling lubricants. |
|  | A6 Metal wiper (32 ... 63 mm) | The cylinder has a hard-chrome-plated piston rod and metal wiper, which scrapes off hard particles (e.g. welding spatter) that stick to the piston rod. For use in welding systems, for example |
| | F1A Recommended for production plants for manufacturing lithium-ion batteries | Suitable for battery production with reduced Cu/Zn/Ni values (F1a) |

Longer service life with bellows kit DADB



The bellows protects the piston rod, the seal and the bearing from the effects of a wide range of media, which has a positive impact on the service life of these components.


The bellows kit is a leak-free system. To prevent unwanted media from being drawn in, the supply and exhaust air for the kit must be ducted via a pressure compensation hole in the connection part [1].

The kit protects the piston rod, seal and bearing against a wide variety of media, for example:

- Dust
- Grease
- Chippings
- Fuel
- Oil

Peripherals overview

DSNU-...



Peripherals overview

| Mounting attachments and accessories | | Piston Ø | DSNU | | | | DSNU-Q | → Page/Internet |
|--------------------------------------|--|-----------|------|----|----|----|------------------|-----------------|
| | | | MA | MQ | MH | KP | | |
| [1] | Round cylinder DSNU | | | | | | | |
| [2] | Hex nut MSK | 16 ... 25 | ■ | ■ | ■ | ■ | ■ | 64 |
| [3] | Bellows kit ²⁾ DADB | 12 ... 63 | ■ | ■ | ■ | – | – | 66 |
| [4] | One-way flow control valve GRLA/GRLZ | 8 ... 63 | ■ | ■ | ■ | ■ | ■ | 75 |
| [5] | Push-in fitting QS | 8 ... 63 | ■ | ■ | ■ | ■ | ■ | 95 |
| [6] | Clevis foot LBN/CRLBN | 8 ... 63 | ■ | – | – | – | ■ | 63 |
| [7] | Foot mounting HBN/CRHBN/CRH | 8 ... 63 | ■ | ■ | ■ | – | ■ | 58 |
| [8] | Flange mounting FBN/CRFBN/CRFV | 8 ... 63 | ■ | ■ | ■ | – | ■ | 60 |
| [9] | Swivel mounting ¹⁾ WBN | 8 ... 63 | ■ | ■ | ■ | – | ■ | 62 |
| [10] | Swivel mounting ¹⁾ SBN | 20 ... 63 | ■ | ■ | ■ | – | ■ Ø 20 ... 50 | 62 |
| [11] | Mounting kit SMBR | 8 ... 63 | ■ | ■ | ■ | ■ | ■ | 72 |
| [12] | Mounting kit SMBR-...S6 | 8 ... 63 | ■ | ■ | ■ | ■ | ■ | 72 |
| [13] | Proximity switch SMT/CRSMT/SDBT | 8 ... 63 | ■ | ■ | ■ | ■ | ■ | 72 |
| | Position transmitter SDAS/SDAT/SMAT | 8 ... 63 | ■ | ■ | ■ | ■ | ■ | 74 |
| [14] | Self-aligning rod coupler FK/CRFK/DARP | 8 ... 63 | ■ | ■ | ■ | ■ | ■ | <?> |
| [15] | Rod clevis SG/CRSG | 8 ... 63 | ■ | ■ | ■ | ■ | ■ | <?> |
| [16] | Coupling piece KSG/KSZ | 12 ... 63 | ■ | ■ | ■ | ■ | ■ | 64 |
| [17] | Rod eye SGS/CRSGS | 8 ... 63 | ■ | ■ | ■ | ■ | ■ | 64 |
| [18] | Right-angle clevis foot LQG | 32 ... 63 | ■ | ■ | ■ | ■ | ■ | 63 |
| [19] | Rod clevis SGA | 32 ... 63 | ■ | ■ | ■ | ■ | ■ | <?> |
| [20] | Clevis foot LBG | 32 ... 63 | ■ | ■ | ■ | ■ | ■ | 65 |
| [21] | Guide unit FEN | 8 ... 25 | ■ | ■ | ■ | – | – | 65 |

 **Note**

- 1) Cannot be used on the bearing cap in combination with protective bellows kit DADB.
- 2) The bellows kit protects the cylinder (piston rod, seal and bearings) against a wide range of media and thus prevents premature wear. It can only be used in combination with an extended piston rod (K8)

Type codes

DSNU-...

| | | |
|------|--|--|
| 001 | Series | |
| DSNU | Round cylinder, double-acting, based on ISO 6432 | |

| | | |
|-----|-----------------|--|
| 002 | Piston diameter | |
| 8 | 8 | |
| 10 | 10 | |
| 12 | 12 | |
| 16 | 16 | |
| 20 | 20 | |
| 25 | 25 | |
| 32 | 32 | |
| 40 | 40 | |
| 50 | 50 | |
| 63 | 63 | |

| | | |
|-----|-----------|--|
| 003 | Stroke | |
| ... | 1 ... 500 | |

| | | |
|-----|---|--|
| 004 | Cushioning | |
| P | Elastic cushioning rings/plates on both sides | |
| PPS | Pneumatic cushioning, self-adjusting at both ends | |
| PPV | Pneumatic cushioning, adjustable at both ends | |

| | | |
|-----|----------------------|--|
| 005 | Position sensing | |
| A | For proximity sensor | |

| | | |
|-----|---|--|
| 006 | Special material properties | |
| | None | |
| F1A | Recommended for production facilities for the manufacture of lithium-ion batteries (Cu<=1%, Zn<=1%, Ni<=1%) | |

| | | |
|-----|---------------------------------|--|
| 007 | Cylinder end cap | |
| | Standard | |
| MA | Axial air connection, end cap | |
| MH | Direct mounting, bearing cap | |
| MQ | Transverse supply port, end cap | |

| | | |
|-----|-----------------------------|--|
| 008 | Protection against rotation | |
| Q | Square piston rod | |
| | None | |

| | | |
|-----|--------------------|--|
| 009 | Piston rod type | |
| | At one end | |
| S2 | Through piston rod | |

| | | |
|-------|-----------------------------|--|
| 010 | Piston rod thread extension | |
| | None | |
| ...K2 | 1 ... 70 mm | |

| | | |
|-----|---------------------------------------|--|
| 011 | K6 - Shortened male piston rod thread | |
| | None | |
| K6 | 1 ... 10 mm | |

| | | |
|-----|------------------------|--|
| 012 | Piston rod thread type | |
| | Male thread | |
| K3 | Female thread | |

| | | |
|---------|---------------|--|
| 013 | Custom thread | |
| "M10"K5 | M10 | |
| "M12"K5 | M12 | |
| "M16"K5 | M16 | |

| | | |
|-------|----------------------|--|
| 014 | Piston rod extension | |
| | None | |
| ...K8 | 1 ... 500 mm | |

| | | |
|-----|---------------|--|
| 015 | Clamping unit | |
| | None | |
| KP | attached | |

| | | |
|-----|----------------------------------|--|
| 016 | Temperature range | |
| | Standard | |
| S6 | Heat-resistant seals max. 120 °C | |

| | | |
|-----|------------------------|--|
| 017 | Constant motion | |
| | Standard | |
| S10 | Uniform, slow movement | |


| | | |
|-----|---------------------------|--|
| 018 | Corrosion protection | |
| | Standard | |
| R3 | High corrosion protection | |

| | | |
|-----|-----------------|--|
| 019 | Scraper variant | |
| | Standard | |
| R8 | Dust protection | |
| A6 | Metal scraper | |


| | | |
|-----|------------------|--|
| 020 | EU certification | |
| | None | |
| EX4 | II 2GD | |

Datasheet


P cushioning



PPV cushioning



PPS cushioning



-  - Diameter
 8 ... 25 mm
 ISO 6432

-  - Diameter
 32 ... 63 mm

-  - Stroke length
 1 ... 500 mm,
 longer strokes on request



| General technical data | | | | | | | | | | | |
|---------------------------|--|----|---|----|-----------|-----------|----------|----------|---------|---------|--|
| Piston Ø | 8 | 10 | 12 | 16 | 20 | 25 | 32 | 40 | 50 | 63 | |
| Conforms to standard | ISO 6432 | | | | | | - | | | | |
| Pneumatic connection | M5 | M5 | M5 | M5 | G1/8 | G1/8 | G1/8 | G1/4 | G1/4 | G3/8 | |
| Piston rod thread | M4 | M4 | M6 | M6 | M8 | M10x1.25 | M10x1.25 | M12x1.25 | M16x1.5 | M16x1.5 | |
| Stroke ¹⁾ [mm] | 1 ... 100 | | 1 ... 200 | | 1 ... 320 | 1 ... 500 | | | | | |
| Design | Piston/piston rod/cylinder barrel | | | | | | | | | | |
| Cushioning | | | | | | | | | | | |
| DSNU-...-P | Elastic cushioning rings/plates at both ends | | | | | | | | | | |
| DSNU-...-PPV | - | | Cushioning, adjustable at both ends | | | | | | | | |
| DSNU-...-PPS | - | | Cushioning, self-adjusting at both ends | | | | | | | | |
| Cushioning length | | | | | | | | | | | |
| DSNU-...-PPV [mm] | - | | 9 | 12 | 15 | 17 | 14 | 18 | 20 | 21 | |
| DSNU-...-PPS [mm] | - | | 12 | 15 | 17 | 14 | 18 | 20 | 21 | | |
| Position sensing | Via proximity switch | | | | | | | | | | |
| Type of mounting | Direct mounting (variant MH only) | | | | | | | | | | |
| | With accessories | | | | | | | | | | |
| Mounting position | Any | | | | | | | | | | |

1) Cylinders with position sensing require a minimum stroke of 10 mm to ensure reliable sensing.
 Longer strokes on request.

Datasheet

| Operating and environmental conditions | | | | | | | | | | | |
|--|-------|--|----|------------|------------|----|------------|------------|------------|----|----|
| Piston Ø | | 8 | 10 | 12 | 16 | 20 | 25 | 32 | 40 | 50 | 63 |
| Operating medium | | Compressed air to ISO 8573-1:2010 [7:4:4] | | | | | | | | | |
| Note on the operating/pilot medium | | Lubricated operation possible (in which case lubricated operation will always be required) | | | | | | | | | |
| Operating pressure ¹⁾ | | | | | | | | | | | |
| DSNU-... | [MPa] | 0.15 ... 1 ³⁾ | | | 0.1 ... 1 | | | | | | |
| | [bar] | 1.5 ... 10 ³⁾ | | | 1 ... 10 | | | | | | |
| DSNU-...-S10 | [MPa] | - | | 0.05 ... 1 | 0.03 ... 1 | | | 0.02 ... 1 | | | |
| | [bar] | - | | 0.5 ... 10 | 0.3 ... 10 | | | 0.2 ... 10 | | | |
| DSNU-...-L ²⁾ | [MPa] | 0.06 ... 1 | | | 0.05 ... 1 | | 0.04 ... 1 | | 0.02 ... 1 | | |
| | [bar] | 0.6 ... 10 | | | 0.5 ... 10 | | 0.4 ... 10 | | 0.2 ... 10 | | |
| DSNU-...-A6 | [MPa] | - | | | | | | 0.2 ... 1 | | | |
| | [bar] | - | | | | | | 2 ... 10 | | | |
| Ambient temperature ⁴⁾ | | | | | | | | | | | |
| DSNU-... | [°C] | -20 ... +80 | | | | | | | | | |
| DSNU-...-S6 | [°C] | 0 ... +120 | | | | | | | | | |
| DSNU-...-S10/L | [°C] | +5 ... +80 | | | | | | | | | |
| DSNU-...-R3 | [°C] | -20 ... +80 | | | | | | | | | |
| DSNU-...-A1 | [°C] | 0 ... +80 | | | | | | | | | |
| DSNU-...-S6-A6 | [°C] | - | | | | | | 0 ... +120 | | | |
| Corrosion resistance class CRC ⁵⁾ | | | | | | | | | | | |
| DSNU-... | | 2 - Moderate corrosion stress | | | | | | | | | |
| DSNU-...-R3 | | 3 - High corrosion stress | | | | | | | | | |
| DSNU-...-F1A | | 0 - no corrosion stress | | | | | | | | | |
| DSNU-...-P/PPV | | See certificate | | | | | | | | - | |

- 1) With variant S2 (through piston rod) or variant KE (stroke adjustment), the minimum operating pressure may increase slightly after an idle period of > 24 hours.
- 2) Values apply only for strokes ≤ 500 mm and after 10 double strokes. In combination with cushioning PPV/PPS, the specifications only apply outside the cushioning range.
- 3) For DSNU-12... PPV (pneumatic cushioning, adjustable at both ends): 0.2 ... 1 MPa (2 ... 10 bar)
- 4) Note operating range of proximity switches.
- 5) More information www.festo.com/x/topic/crc

| ATEX ¹⁾ | |
|---|---|
| ATEX category for gas | II 2G |
| Type of (ignition) protection for gas | Ex h IIC T4 Gb |
| ATEX category for dust | II 2D |
| Type of ignition protection for dust | Ex h IIIC T120°C Db |
| Explosion-proof ambient temperature | -20 °C ≤ Ta ≤ +60 °C |
| CE marking (see declaration of conformity) | To EU Explosion Protection Directive (ATEX) |
| UKCA marking (see declaration of conformity) | To UK explosion regulations |
| Explosion protection certification outside the EU | EPL Db (GB) |
| | EPL Gb (GB) |

- 1) Note the ATEX certification of the accessories.

| Weight [g] | | | | | | | | | | | |
|------------------------------------|--------|------|------|------|------|-------|-----|-------|-----|------|------|
| Piston Ø | | 8 | 10 | 12 | 16 | 20 | 25 | 32 | 40 | 50 | 63 |
| DSNU-... | | | | | | | | | | | |
| Product weight with 0 mm stroke | | 34.6 | 37.3 | 75 | 89.9 | 186.8 | 238 | 370.5 | 661 | 1087 | 1445 |
| Additional weight per 10 mm stroke | | 2.4 | 2.7 | 4 | 4.6 | 7.2 | 11 | 15.5 | 24 | 40 | 44 |
| Moving mass with 0 mm stroke | | 7.5 | 8.5 | 18.5 | 23 | 44 | 71 | 121 | 230 | 413 | 459 |
| Moving mass per 10 mm stroke | | 1 | 1 | 2 | 2 | 4 | 6 | 9 | 16 | 25 | 25 |
| DSNU-...-S2 | | | | | | | | | | | |
| Moving mass with 0 mm stroke | | 12 | 12.5 | 30 | 34.5 | 70 | 113 | 182 | 363 | 638 | 701 |
| Moving mass per 10 mm stroke | | 2 | 2 | 4 | 4 | 8 | 12 | 18 | 32 | 50 | 50 |
| DSNU-...-KE | | | | | | | | | | | |
| Moving mass with 0 mm stroke | [15KE] | 17 | 17.5 | - | - | - | - | - | - | - | - |
| | [25KE] | - | - | 46 | 50.5 | 99 | 142 | 251 | 469 | 839 | 902 |
| | [50KE] | - | - | - | - | - | - | - | 491 | 918 | 981 |
| Moving mass per 10 mm stroke | | 2 | 2 | 4 | 4 | 8 | 12 | 18 | 32 | 50 | 50 |

Datasheet

| Speed [mm/s] ¹⁾ | | | | | | | |
|--|------------|----|----|-----------|----|----|-----------|
| Piston Ø | 16 | 20 | 25 | 32 | 40 | 50 | 63 |
| Speed with stick-slip-free operation, horizontal, without load, at 0.6 MPa (6 bar) | 10 ... 100 | | | 8 ... 100 | | | 5 ... 100 |

1) Measurements of less than 1 mm/s were not conducted

| Forces [N] and impact energy [J] | | | | | | | | | | |
|---|-------|-------|-------|-------|------|------|------|------|------|------|
| Piston Ø | 8 | 10 | 12 | 16 | 20 | 25 | 32 | 40 | 50 | 63 |
| Theoretical force at 0.6 MPa (6 bar), advancing | 30 | 47 | 68 | 121 | 189 | 295 | 483 | 753 | 1178 | 1870 |
| Theoretical force at 0.6 MPa (6 bar), retracting | 23 | 40 | 51 | 104 | 158 | 247 | 415 | 633 | 990 | 1682 |
| Impact energy in the end positions for P cushioning ¹⁾ | | | | | | | | | | |
| DSNU-... | 0.03 | 0.05 | 0.07 | 0.15 | 0.2 | 0.3 | 0.4 | 0.7 | 1 | 1.3 |
| DSNU-...-S6 | 0.015 | 0.025 | 0.035 | 0.075 | 0.1 | 0.15 | 0.2 | 0.35 | 0.5 | 0.65 |
| DSNU-...-KE | 0.025 | 0.025 | 0.055 | 0.12 | 0.16 | 0.24 | 0.32 | 0.56 | 0.8 | 1 |





1) The values are reduced by approx. 50% at an ambient temperature of 80 °C

Permissible impact velocity:
$$V = \sqrt{\frac{2 \times E}{m_1 + m_2}}$$

Maximum permissible mass:
$$m_2 = \frac{2 \times E}{V^2} - m_1$$

V Perm. impact velocity
 E Max. impact energy
 m1 Moving mass (drive)
 m2 Moving payload


Average piston speed v as a function of payload m in combination with cushioning PPS



Datasheet


Average piston speed v as a function of payload m in combination with cushioning PPS

Piston \varnothing 40




- DSNU-40-50
- ⋯ DSNU-40-100
- - - DSNU-40-200

Piston \varnothing 50



- DSNU-50-50
- ⋯ DSNU-50-100
- - - DSNU-50-200

Piston \varnothing 63



- DSNU-63-50
- ⋯ DSNU-63-100
- - - DSNU-63-200


Note:

Engineering software for
 P cushioning
 PPV cushioning
 PPS cushioning
 → <https://www.festo.com/x/pneumatic-sizing>



Average piston speed = Stroke/
 movement time

Datasheet

Max. transverse force F_q as a function of projection l





DSNU-...



- DSNU-8/10
- · - · - DSNU-12/16
- - - DSNU-20
- · · · · DSNU-25

- · - · - DSNU-32
- - - DSNU-40
- - - DSNU-50/63

DSNU-...-S2 – Through piston rod




- DSNU-8/10
- · - · - DSNU-12/16
- - - DSNU-20
- · · · · DSNU-25

- · - · - DSNU-32
- - - DSNU-40
- - - DSNU-50/63

Datasheet

Materials

Sectional view



| Round cylinder | 8 ... 25 | 32 ... 63 |
|-------------------------------|--|-----------------------------------|
| [1] Piston rod | | |
| DSNU-... | High-alloy steel | |
| DSNU-...-R3 | High-alloy stainless steel | |
| DSNU-...-A6 | – | Hard-chrome-plated tempered steel |
| [2] Piston rod bearing | Sintered bronze | |
| [3] Bearing cap | Wrought aluminium alloy, colourless anodised | |
| [4] Cylinder barrel | High-alloy stainless steel | |
| [5] End cap | Wrought aluminium alloy, colourless anodised | |
| [6] Swivel bearing | Polymer | |
| – Piston rod wiper seal | | |
| DSNU-... | TPE-U(PU) | |
| DSNU-...-S6/-S10/-L/-A1 | FPM | |
| DSNU-...-R3 | TPE-U (PU) media seal (modified for resistance to hydrolysis and cleaning) | |
| Piston rod scraper | | |
| DSNU-...-A6 | – | CuZn |
| Stroke adjustment DSNU-...-KE | | |
| Stop element | PE-UHMW | |
| Threaded coupling | Anodised aluminium | |
| LABS (PWIS) conformity | VDMA24364-B1/B2-L ¹⁾ | |
| Cleanroom class | Class 6 to ISO 14644-1 | |
| Note on materials | | |
| DSNU-... | RoHs-compliant | |
| DSNU-...-S10 | Contains paint-wetting impairment substances | |
| DSNU-...-F1A | Suitable for battery production with reduced Cu/Zn/Ni values (F1a) | |


1) Applies to all variants except S10

Datasheet

Dimensions

Download CAD data → www.festo.com

DSNU-8 ... 25



-  - **Note**
 Piston rod nut is not included in the scope of delivery for diameter 8 ... 20.
 + = plus stroke length

| ∅ [mm] | AM | B ∅ h8 | BE | BF | CD ∅ H9 | D ∅ | D4 ∅ | E | EE | EW | G |
|-----------|----|--------------|----------|----|---------------|--------|---------|----|------|----|------|
| 8 | 12 | 12 | M12x1.25 | 12 | 4 | 16 | 9.3 | 14 | M5 | 8 | 10 |
| 10 | | | | | | | 11.3 | | | | |
| 12 | 16 | 16 | M16x1.5 | 17 | 6 | 20 | 13.3 | 18 | G1/8 | 12 | 16 |
| 16 | | | | | | | 17.3 | | | | |
| 20 | 20 | 22 | M22x1.5 | 20 | 8 | 30 | 21.3 | 26 | 16 | 16 | |
| 25 | 22 | | | 22 | | | 22 | | | | 26.5 |

| ∅ [mm] | KK | KV | KW | MM ∅ | L | L2 | PL | VD | WF ±1.2 | XC ±1 | ZJ | ∅1 |
|-----------|----------|----|----|---------|----|------|-----|----|------------|----------|----|----|
| 8 | M4 | 19 | 6 | 4 | 6 | 46 | 6 | 2 | 16 | 64 | 62 | - |
| 10 | | | | | | 50 | | | | | | |
| 12 | M6 | 24 | 8 | 6 | 9 | 56 | 6 | 2 | 22 | 75 | 72 | 5 |
| 16 | | | | | | 68 | | | | | | |
| 20 | M8 | 32 | 11 | 8 | 12 | 68 | 8.2 | 2 | 24 | 95 | 92 | 7 |
| 25 | M10x1.25 | | | 10 | | 69.5 | | | | | | |


Datasheet

Dimensions


Download CAD data → www.festo.com

DSNU-8 ... 25


MQ – Lateral supply port, short end cap



MA – Axial supply port, short end cap



MH – With direct mounting



+ = plus stroke length

Datasheet

| ø [mm] | B ø h8 | D2 ø | D3 ø | E | EE | F | FB ø | G | L2 | | |
|-----------|--------------|---------|---------|----|------|-----|---------|------|----------|------|------|
| | | | | | | | | | DSNU-... | | |
| | | | | | | | | | -MQ | -MA | -MH |
| 8 | 12 | 10.5 | 6 | 24 | M5 | 3 | 3.4 | 10 | 46 | 43.6 | 53.5 |
| 10 | | 12.5 | | | | | | | | 43.1 | 53.8 |
| 12 | 16 | 14.5 | 8 | 30 | | | 4.5 | | 50 | 47.7 | 62 |
| 16 | | 17.5 | | | | | | | | 53.7 | 67.8 |
| 20 | 22 | 21.7 | 10 | 40 | G1/8 | 5.5 | 16 | 68 | 66.5 | 81.5 | |
| 25 | | 26.7 | 11 | | | 6.6 | | 69.5 | 68.5 | 86.2 | |

| ø [mm] | L3 | L4 | L5 | R | RT | TG | T1 | U0 | WF | ZJ | | |
|-----------|------|-----|------|----|----|----|-----|----|----|----------|------|------|
| | | | | | | | | | | DSNU-... | | |
| | | | | | | | | | | -MQ | -MA | -MH |
| 8 | 7.6 | 5 | 14 | 12 | M3 | 18 | 3.4 | 16 | 8 | 62 | 59.6 | 61.5 |
| 10 | 7.1 | | | | | | | | | | 59.1 | 61.8 |
| 12 | 7.7 | 6 | 18.1 | 16 | M4 | 23 | 4.5 | 22 | 10 | 72 | 69.7 | 72 |
| 16 | | | | | | | | | | 78 | 75.7 | 77.8 |
| 20 | 14.5 | 7.5 | 22.4 | 22 | M5 | 31 | 5.5 | 28 | 11 | 92 | 90.5 | 91.5 |
| 25 | 14 | | 25.2 | 25 | | | 6.6 | | | 32 | 97.5 | 96.5 |


Datasheet

Dimensions

Download CAD data → www.festo.com

DSNU-8 ... 25

S2 – Through piston rod




Note

The thread types at both piston rod ends are identical. In combination with variant Q, the left piston rod end is square, the right piston rod end round.


- + = plus stroke length
- ++ = plus 2x stroke length

KE – Stroke adjustment




- + = plus stroke length
- ++ = plus 2x stroke length


K2 – Extended male piston rod thread




K6 – Shortened male piston rod thread




K3 – Female piston rod thread



K5 – Special piston rod thread



K8 – Extended piston rod



Note

If variant K8 is required in combination with S2, the piston rod will only be extended at one end.

Datasheet

| ∅ [mm] | A1 max. | A2 max. | A3 max. | A5 | | AF | AM | D8 ∅ | KF | KK | |
|-----------|------------|------------|------------|----------|-------|----|----|---------|----------|--------------|---------------------------------|
| | | | | DSNU-... | | | | | | Basic thread | Special thread ¹⁾ |
| | | | | -15KE | -25KE | | | | | | |
| 8 | 15 | 50 | 4 | 27.5 | - | - | 12 | 12 | - | M4 | - |
| 10 | | | | | | - | | | - | | |
| 12 | 20 | 100 | | - | 43 | - | 16 | 15 | - | M6 | - |
| 16 | | | | | | - | | | - | | |
| 20 | 25 | 110 | 8 | - | 47 | 12 | 20 | 20 | M4 | M8 | - |
| 25 | 35 | 150 | | | | 22 | M6 | | M10x1.25 | M10 | |

1) The special threads are only available as male threads. The scope of delivery does not include a hex nut for the piston rod thread


| ∅ [mm] | L13 +1 | T4 | WF ±1.2 | ZJ | | | ZM | ⊖ 2 | ⊖ 3 |
|-----------|-----------|-----|------------|----------|------|------|-------|-----|-----|
| | | | | DSNU-... | | | | | |
| | | | | -MQ | -MA | -MH | | | |
| 8 | 78 | - | 16 | 62 | 59.6 | 61.5 | 78.4 | 7 | 10 |
| 10 | | - | | | 59.1 | 61.8 | | | |
| 12 | 94 | - | 22 | 72 | 69.7 | 72 | 94 | 10 | 13 |
| 16 | 100 | - | | 78 | 75.7 | 77.8 | | | |
| 20 | 116 | 2 | 24 | 92 | 90.5 | 91.5 | 116 | 13 | 17 |
| 25 | 125.5 | 2.6 | 28 | 97.5 | 96.5 | 97.2 | 125.5 | | |

Datasheet

Dimensions

Download CAD data → www.festo.com

DSNU-32 ... 63



| ∅ | AM | B ∅ h8 | BE | BF | B4 | CD ∅ H9 | D ∅ | D1 ∅ | D4 ∅ | E | EE | EW |
|----|----|--------------|---------|----|----|---------------|--------|---------|---------|----|------|------|
| 32 | 22 | 30 | M30x1.5 | 26 | 5 | 10 | 41 | 42 | 33.6 | 38 | G1/8 | 16 |
| 40 | 24 | 38 | M38x1.5 | 30 | 6 | 12 | 49 | 50 | 41.6 | 45 | G1/4 | 18 |
| 50 | 32 | 45 | M45x1.5 | 33 | 8 | 16 | 57 | 60 | 52.4 | - | | G3/8 |
| 63 | | | | | | | 70 | | 65.4 | | | |

| ∅ | G | KK | KW | MM ∅ | L | L2 | PL | VD | WF ±1.2 | XC ±1 | ZJ | ⊖1 | ⊖2 |
|----|----|----------|----|---------|----|------|----|----|------------|----------|-------|----|----|
| 32 | 19 | M10x1.25 | 8 | 12 | 13 | 69.5 | 9 | 2 | 34 | 117.5 | 103.5 | 10 | 16 |
| 40 | 25 | M12x1.25 | 10 | 16 | 15 | 84.6 | 12 | 3 | 39 | 139.6 | 123.6 | 13 | 18 |
| 50 | | M16x1.5 | | 20 | 16 | 86.2 | | | 44 | 147.2 | 130.2 | 17 | 24 |
| 63 | 28 | | | | | 94.2 | 13 | 45 | 156.2 | 139.2 | | | |


Datasheet

Dimensions


Download CAD data → www.festo.com

DSNU-32 ... 63


MQ – Lateral supply port, short end cap



MA – Axial supply port, short end cap



MH – With direct mounting



[1] Centring holes
(2 centring sleeves included in the scope of delivery)
+ = plus stroke length

| ∅ [mm] | B ∅ h8 | B2 | E | EE | G | F | FB ∅ | D2 ∅ | D3 ∅ | D5 ∅ | D6 ∅ | L1 | L2 | | |
|-----------|--------------|----|----|------|----|----|---------|---------|---------|---------|---------|------|----------|-------|-------|
| | | | | | | | | | | | | | DSNU-... | | |
| | | | | | | | | | | | | | -MQ | -MA | -MH |
| 32 | 30 | 1 | 48 | G1/8 | 19 | 4 | 6.6 | 34 | 11 | 9 | 30 | 3 | 69.5 | 65.5 | 85.5 |
| 40 | 38 | | 54 | G1/4 | 25 | | 9 | 42 | 14 | 12 | 38 | 4 | 84.6 | 77.6 | 104.6 |
| 50 | 45 | 64 | 11 | | | 53 | 15 | 45 | | | | | 86.2 | 86.2 | 109.2 |
| 63 | | 2 | 72 | G3/8 | 28 | 11 | 66 | 18 | 15 | 45 | 4 | 94.2 | 94.2 | 117.2 | |


| ∅ [mm] | L3 | L4 | L5 | R | RT | T0 | T1 | T2 | TG | U0 | WF | ZJ | | |
|-----------|----|----|----|----|----|----|-----|-----|----|----|-------|----------|-------|-------|
| | | | | | | | | | | | | DSNU-... | | |
| | | | | | | | | | | | | -MQ | -MA | -MH |
| 32 | 15 | 12 | 25 | 30 | M5 | 19 | 6.6 | 2.1 | 38 | 40 | 12 | 103.5 | 99.5 | 97.5 |
| 40 | 18 | 15 | 32 | 38 | | 24 | 9 | 2.6 | 42 | 48 | | 123.6 | 116.6 | 116.6 |
| 50 | 25 | | 35 | 42 | M6 | 32 | 9 | 3.1 | 50 | 58 | 15 | 130.2 | 130.2 | 124.2 |
| 63 | 28 | 36 | 44 | M8 | 36 | 11 | 3.1 | 52 | 72 | 15 | 139.2 | 139.2 | 132.2 | |

Datasheet

Dimensions

Download CAD data → www.festo.com

DSNU-32 ... 63
S2 – Through piston rod




Note

The thread types at both piston rod ends are identical. In combination with variant Q, the left piston rod end is square, the right piston rod end round.


- + = plus stroke length
- ++ = plus 2x stroke length

KE – Stroke adjustment




- + = plus stroke length
- ++ = plus 2x stroke length


K2 – Extended male piston rod thread




K6 – Shortened male piston rod thread




K3 – Female piston rod thread



K5 – Special piston rod thread



K8 – Extended piston rod



Note

If variant K8 is required in combination with S2, the piston rod will only be extended at one end.

Datasheet

| ∅ [mm] | A1 max. | A2 max. | A3 max. | A5 | | AF | AM | D8 ∅ | KF | KK | |
|-----------|------------|------------|------------|----------|-------|----|----|---------|-----|--------------|---------------------------------|
| | | | | DSNU-... | | | | | | Basic thread | Special thread ¹⁾ |
| | | | | -25KE | -50KE | | | | | | |
| 32 | 35 | 500 | 8 | 52 | - | 12 | 22 | 30 | M6 | M10x1.25 | M10 |
| 40 | | | | 56 | 81 | | 24 | 35 | M8 | M12x1.25 | M12 |
| 50 | 70 | | 10 | 67 | 92 | 16 | 32 | 45 | M10 | M16x1.5 | M16 |
| 63 | | | | | | | | | | | |

1) The special threads are only available as male threads. The scope of delivery does not include a hex nut for the piston rod thread

| ∅ [mm] | L13 +1 | T4 | WF ±1.2 | ZJ | | | ZM | ⊖ 2 | ⊖ 3 |
|-----------|-----------|-----|------------|----------|-------|-------|-------|-----|-----|
| | | | | DSNU-... | | | | | |
| | | | | -MQ | -MA | -MH | | | |
| 32 | 137.5 | 2.6 | 34 | 103.5 | 99.5 | 97.5 | 137.5 | 17 | 24 |
| 40 | 162.6 | 3.3 | 39 | 123.6 | 111.6 | 116.6 | 162.6 | 19 | 30 |
| 50 | 174.2 | 4.7 | 44 | 130.2 | 130.2 | 124.2 | 174.2 | 24 | |
| 63 | 184.2 | | 45 | 139.2 | 139.2 | 132.2 | 184.2 | | |

Datasheet

| Ordering data | | | | PPV – Pneumatic cushioning, adjustable at both ends | | PPS – Pneumatic cushioning, self-adjusting at both ends | |
|---------------|--------|--|---------------------------|---|-------------------|---|-------------------|
| Piston Ø | Stroke | P – Elastic cushioning rings/plates at both ends | A – With position sensing | A – With position sensing | | A – With position sensing | |
| [mm] | [mm] | Part no. | Type | Part no. | Type | Part no. | Type |
| 8 | 10 | 19177 | DSNU-8-10-P-A | - | | - | |
| | 15 | 1908247 | DSNU-8-15-P-A | | | | |
| | 20 | 1908248 | DSNU-8-20-P-A | | | | |
| | 25 | 19178 | DSNU-8-25-P-A | | | | |
| | 30 | 1908249 | DSNU-8-30-P-A | | | | |
| | 40 | 19179 | DSNU-8-40-P-A | | | | |
| | 50 | 19180 | DSNU-8-50-P-A | | | | |
| | 60 | 1908250 | DSNU-8-60-P-A | | | | |
| | 80 | 19181 | DSNU-8-80-P-A | | | | |
| 100 | 19182 | DSNU-8-100-P-A | | | | | |
| 10 | 10 | 19183 | DSNU-10-10-P-A | - | | - | |
| | 15 | 1908251 | DSNU-10-15-P-A | | | | |
| | 20 | 1908252 | DSNU-10-20-P-A | | | | |
| | 25 | 19184 | DSNU-10-25-P-A | | | | |
| | 30 | 1908253 | DSNU-10-30-P-A | | | | |
| | 40 | 19185 | DSNU-10-40-P-A | | | | |
| | 50 | 19186 | DSNU-10-50-P-A | | | | |
| | 60 | 1908254 | DSNU-10-60-P-A | | | | |
| | 80 | 19187 | DSNU-10-80-P-A | | | | |
| 100 | 19188 | DSNU-10-100-P-A | | | | | |
| 12 | 10 | 19189 | DSNU-12-10-P-A | - | | - | |
| | 15 | 1908255 | DSNU-12-15-P-A | | | | |
| | 20 | 1908256 | DSNU-12-20-P-A | | | | |
| | 25 | 19190 | DSNU-12-25-P-A | | | | |
| | 30 | 1908257 | DSNU-12-30-P-A | | | | |
| | 40 | 19191 | DSNU-12-40-P-A | | | | |
| | 50 | 19192 | DSNU-12-50-P-A | | | | |
| | 60 | 1908258 | DSNU-12-60-P-A | | | | |
| | 70 | 5249943 | DSNU-12-70-P-A | | | | |
| | 80 | 19193 | DSNU-12-80-P-A | | | | |
| | 100 | 19194 | DSNU-12-100-P-A | | | | |
| | 125 | 19195 | DSNU-12-125-P-A | | | | |
| | 150 | 5249947 | DSNU-12-150-P-A | | | | |
| | 160 | 19196 | DSNU-12-160-P-A | | | | |
| 200 | 19197 | DSNU-12-200-P-A | | | | | |
| 16 | 10 | 19198 | DSNU-16-10-P-A | 1908266 | DSNU-16-10-PPV-A | 1908274 | DSNU-16-10-PPS-A |
| | 15 | 1908259 | DSNU-16-15-P-A | 1908267 | DSNU-16-15-PPV-A | 1908275 | DSNU-16-15-PPS-A |
| | 20 | 1908260 | DSNU-16-20-P-A | 1908268 | DSNU-16-20-PPV-A | 1908276 | DSNU-16-20-PPS-A |
| | 25 | 19199 | DSNU-16-25-P-A | 33973 | DSNU-16-25-PPV-A | 559263 | DSNU-16-25-PPS-A |
| | 30 | 1908261 | DSNU-16-30-P-A | 1908269 | DSNU-16-30-PPV-A | 1908277 | DSNU-16-30-PPS-A |
| | 35 | 1908262 | DSNU-16-35-P-A | 1908270 | DSNU-16-35-PPV-A | 1908278 | DSNU-16-35-PPS-A |
| | 40 | 19200 | DSNU-16-40-P-A | 19229 | DSNU-16-40-PPV-A | 559264 | DSNU-16-40-PPS-A |
| | 50 | 19201 | DSNU-16-50-P-A | 19230 | DSNU-16-50-PPV-A | 559265 | DSNU-16-50-PPS-A |
| | 60 | 1908263 | DSNU-16-60-P-A | 1908271 | DSNU-16-60-PPV-A | 1908279 | DSNU-16-60-PPS-A |
| | 70 | 1908264 | DSNU-16-70-P-A | 1908272 | DSNU-16-70-PPV-A | 1908280 | DSNU-16-70-PPS-A |
| | 80 | 19202 | DSNU-16-80-P-A | 19231 | DSNU-16-80-PPV-A | 559266 | DSNU-16-80-PPS-A |
| | 100 | 19203 | DSNU-16-100-P-A | 19232 | DSNU-16-100-PPV-A | 559267 | DSNU-16-100-PPS-A |
| | 125 | 19204 | DSNU-16-125-P-A | 19233 | DSNU-16-125-PPV-A | 559268 | DSNU-16-125-PPS-A |
| | 150 | 1908265 | DSNU-16-150-P-A | 1908273 | DSNU-16-150-PPV-A | 1908281 | DSNU-16-150-PPS-A |
| | 160 | 19205 | DSNU-16-160-P-A | 19234 | DSNU-16-160-PPV-A | 559269 | DSNU-16-160-PPS-A |
| | 200 | 19206 | DSNU-16-200-P-A | 19235 | DSNU-16-200-PPV-A | 559270 | DSNU-16-200-PPS-A |

Datasheet

| Ordering data | | | | | | | | | | | |
|---------------|--------|--|-----------------|---|-------------------|---|-------------------|--|--|--|--|
| Piston Ø | Stroke | P – Elastic cushioning rings/plates at both ends | | PPV – Pneumatic cushioning, adjustable at both ends | | PPS – Pneumatic cushioning, self-adjusting at both ends | | | | | |
| [mm] | [mm] | A – With position sensing | | A – With position sensing | | A – With position sensing | | | | | |
| | | Part no. | Type | Part no. | Type | Part no. | Type | | | | |
| 20 | 10 | 19207 | DSNU-20-10-P-A | 1908289 | DSNU-20-10-PPV-A | 1908297 | DSNU-20-10-PPS-A | | | | |
| | 15 | 1908282 | DSNU-20-15-P-A | 1908290 | DSNU-20-15-PPV-A | 1908298 | DSNU-20-15-PPS-A | | | | |
| | 20 | 1908283 | DSNU-20-20-P-A | 1908291 | DSNU-20-20-PPV-A | 1908299 | DSNU-20-20-PPS-A | | | | |
| | 25 | 19208 | DSNU-20-25-P-A | 33974 | DSNU-20-25-PPV-A | 559271 | DSNU-20-25-PPS-A | | | | |
| | 30 | 1908284 | DSNU-20-30-P-A | 1908292 | DSNU-20-30-PPV-A | 1908300 | DSNU-20-30-PPS-A | | | | |
| | 35 | 1908285 | DSNU-20-35-P-A | 1908293 | DSNU-20-35-PPV-A | 1908301 | DSNU-20-35-PPS-A | | | | |
| | 40 | 19209 | DSNU-20-40-P-A | 19236 | DSNU-20-40-PPV-A | 559272 | DSNU-20-40-PPS-A | | | | |
| | 50 | 19210 | DSNU-20-50-P-A | 19237 | DSNU-20-50-PPV-A | 559273 | DSNU-20-50-PPS-A | | | | |
| | 60 | 1908286 | DSNU-20-60-P-A | 1908294 | DSNU-20-60-PPV-A | 1908302 | DSNU-20-60-PPS-A | | | | |
| | 70 | 1908287 | DSNU-20-70-P-A | 1908295 | DSNU-20-70-PPV-A | 1908303 | DSNU-20-70-PPS-A | | | | |
| | 80 | 19211 | DSNU-20-80-P-A | 19238 | DSNU-20-80-PPV-A | 559274 | DSNU-20-80-PPS-A | | | | |
| | 100 | 19212 | DSNU-20-100-P-A | 19239 | DSNU-20-100-PPV-A | 559275 | DSNU-20-100-PPS-A | | | | |
| | 125 | 19213 | DSNU-20-125-P-A | 19240 | DSNU-20-125-PPV-A | 559276 | DSNU-20-125-PPS-A | | | | |
| | 150 | 1908288 | DSNU-20-150-P-A | 1908296 | DSNU-20-150-PPV-A | 1908304 | DSNU-20-150-PPS-A | | | | |
| | 160 | 19214 | DSNU-20-160-P-A | 19241 | DSNU-20-160-PPV-A | 559277 | DSNU-20-160-PPS-A | | | | |
| | 200 | 19215 | DSNU-20-200-P-A | 19242 | DSNU-20-200-PPV-A | 559278 | DSNU-20-200-PPS-A | | | | |
| | 250 | 19216 | DSNU-20-250-P-A | 19243 | DSNU-20-250-PPV-A | 559279 | DSNU-20-250-PPS-A | | | | |
| | 300 | 19217 | DSNU-20-300-P-A | 19244 | DSNU-20-300-PPV-A | 559280 | DSNU-20-300-PPS-A | | | | |
| 320 | 34718 | DSNU-20-320-P-A | 34720 | DSNU-20-320-PPV-A | 559281 | DSNU-20-320-PPS-A | | | | | |
| 25 | 10 | 19218 | DSNU-25-10-P-A | 1908312 | DSNU-25-10-PPV-A | 1908320 | DSNU-25-10-PPS-A | | | | |
| | 15 | 1908305 | DSNU-25-15-P-A | 1908313 | DSNU-25-15-PPV-A | 1908321 | DSNU-25-15-PPS-A | | | | |
| | 20 | 1908306 | DSNU-25-20-P-A | 1908314 | DSNU-25-20-PPV-A | 1908322 | DSNU-25-20-PPS-A | | | | |
| | 25 | 19219 | DSNU-25-25-P-A | 33975 | DSNU-25-25-PPV-A | 559282 | DSNU-25-25-PPS-A | | | | |
| | 30 | 1908307 | DSNU-25-30-P-A | 1908315 | DSNU-25-30-PPV-A | 1908323 | DSNU-25-30-PPS-A | | | | |
| | 35 | 1908308 | DSNU-25-35-P-A | 1908316 | DSNU-25-35-PPV-A | 1908324 | DSNU-25-35-PPS-A | | | | |
| | 40 | 19220 | DSNU-25-40-P-A | 19245 | DSNU-25-40-PPV-A | 559283 | DSNU-25-40-PPS-A | | | | |
| | 50 | 19221 | DSNU-25-50-P-A | 19246 | DSNU-25-50-PPV-A | 559284 | DSNU-25-50-PPS-A | | | | |
| | 60 | 1908309 | DSNU-25-60-P-A | 1908317 | DSNU-25-60-PPV-A | 1908325 | DSNU-25-60-PPS-A | | | | |
| | 70 | 1908310 | DSNU-25-70-P-A | 1908318 | DSNU-25-70-PPV-A | 1908326 | DSNU-25-70-PPS-A | | | | |
| | 80 | 19222 | DSNU-25-80-P-A | 19247 | DSNU-25-80-PPV-A | 559285 | DSNU-25-80-PPS-A | | | | |
| | 100 | 19223 | DSNU-25-100-P-A | 19248 | DSNU-25-100-PPV-A | 559286 | DSNU-25-100-PPS-A | | | | |
| | 125 | 19224 | DSNU-25-125-P-A | 19249 | DSNU-25-125-PPV-A | 559287 | DSNU-25-125-PPS-A | | | | |
| | 150 | 1908311 | DSNU-25-150-P-A | 1908319 | DSNU-25-150-PPV-A | 1908327 | DSNU-25-150-PPS-A | | | | |
| | 160 | 19225 | DSNU-25-160-P-A | 19250 | DSNU-25-160-PPV-A | 559288 | DSNU-25-160-PPS-A | | | | |
| | 200 | 19226 | DSNU-25-200-P-A | 19251 | DSNU-25-200-PPV-A | 559289 | DSNU-25-200-PPS-A | | | | |
| | 250 | 19227 | DSNU-25-250-P-A | 19252 | DSNU-25-250-PPV-A | 559290 | DSNU-25-250-PPS-A | | | | |
| | 300 | 19228 | DSNU-25-300-P-A | 19253 | DSNU-25-300-PPV-A | 559291 | DSNU-25-300-PPS-A | | | | |
| 320 | 34719 | DSNU-25-320-P-A | 34721 | DSNU-25-320-PPV-A | 559292 | DSNU-25-320-PPS-A | | | | | |
| 400 | 35191 | DSNU-25-400-P-A | 35193 | DSNU-25-400-PPV-A | 559293 | DSNU-25-400-PPS-A | | | | | |
| 500 | 35192 | DSNU-25-500-P-A | 35194 | DSNU-25-500-PPV-A | 559294 | DSNU-25-500-PPS-A | | | | | |

Datasheet

| Ordering data | | | | PPV – Pneumatic cushioning, adjustable at both ends | | PPS – Pneumatic cushioning, self-adjusting at both ends | |
|---------------|--------|--|---------------------------|---|-------------------|---|-------------------|
| Piston Ø | Stroke | P – Elastic cushioning rings/plates at both ends | A – With position sensing | A – With position sensing | | A – With position sensing | |
| [mm] | [mm] | Part no. | Type | Part no. | Type | Part no. | Type |
| 32 | 10 | 5249365 | DSNU-32-10-P-A | – | | – | |
| | 15 | 5249366 | DSNU-32-15-P-A | – | | – | |
| | 20 | 5249367 | DSNU-32-20-P-A | – | | – | |
| | 25 | 195980 | DSNU-32-25-P-A | 196020 | DSNU-32-25-PPV-A | 559295 | DSNU-32-25-PPS-A |
| | 30 | 5249368 | DSNU-32-30-P-A | 5249851 | DSNU-32-30-PPV-A | 5249968 | DSNU-32-30-PPS-A |
| | 40 | 195981 | DSNU-32-40-P-A | 196021 | DSNU-32-40-PPV-A | 559296 | DSNU-32-40-PPS-A |
| | 50 | 195982 | DSNU-32-50-P-A | 196022 | DSNU-32-50-PPV-A | 559297 | DSNU-32-50-PPS-A |
| | 60 | 5249369 | DSNU-32-60-P-A | 5249853 | DSNU-32-60-PPV-A | 5249970 | DSNU-32-60-PPS-A |
| | 70 | 5249370 | DSNU-32-70-P-A | 5249854 | DSNU-32-70-PPV-A | 5249971 | DSNU-32-70-PPS-A |
| | 80 | 195983 | DSNU-32-80-P-A | 196023 | DSNU-32-80-PPV-A | 559298 | DSNU-32-80-PPS-A |
| | 100 | 195984 | DSNU-32-100-P-A | 196024 | DSNU-32-100-PPV-A | 559299 | DSNU-32-100-PPS-A |
| | 125 | 195985 | DSNU-32-125-P-A | 196025 | DSNU-32-125-PPV-A | 559300 | DSNU-32-125-PPS-A |
| | 150 | 5249371 | DSNU-32-150-P-A | 5249855 | DSNU-32-150-PPV-A | 5249972 | DSNU-32-150-PPS-A |
| | 160 | 195986 | DSNU-32-160-P-A | 196026 | DSNU-32-160-PPV-A | 559301 | DSNU-32-160-PPS-A |
| | 200 | 195987 | DSNU-32-200-P-A | 196027 | DSNU-32-200-PPV-A | 559302 | DSNU-32-200-PPS-A |
| | 250 | 195988 | DSNU-32-250-P-A | 196028 | DSNU-32-250-PPV-A | 559303 | DSNU-32-250-PPS-A |
| | 300 | 5249372 | DSNU-32-300-P-A | 5249856 | DSNU-32-300-PPV-A | 5249973 | DSNU-32-300-PPS-A |
| 320 | 195989 | DSNU-32-320-P-A | 196029 | DSNU-32-320-PPV-A | 559304 | DSNU-32-320-PPS-A | |
| 40 | 10 | 5262529 | DSNU-40-10-P-A | – | | – | |
| | 15 | 5262530 | DSNU-40-15-P-A | – | | – | |
| | 20 | 5262531 | DSNU-40-20-P-A | – | | – | |
| | 25 | 195990 | DSNU-40-25-P-A | 196030 | DSNU-40-25-PPV-A | 559305 | DSNU-40-25-PPS-A |
| | 30 | 5262532 | DSNU-40-30-P-A | 5262705 | DSNU-40-30-PPV-A | 5262768 | DSNU-40-30-PPS-A |
| | 40 | 195991 | DSNU-40-40-P-A | 196031 | DSNU-40-40-PPV-A | 559306 | DSNU-40-40-PPS-A |
| | 50 | 195992 | DSNU-40-50-P-A | 196032 | DSNU-40-50-PPV-A | 559307 | DSNU-40-50-PPS-A |
| | 60 | 5262534 | DSNU-40-60-P-A | 5262706 | DSNU-40-60-PPV-A | 5262769 | DSNU-40-60-PPS-A |
| | 70 | 5262535 | DSNU-40-70-P-A | 5262707 | DSNU-40-70-PPV-A | 5262771 | DSNU-40-70-PPS-A |
| | 80 | 195993 | DSNU-40-80-P-A | 196033 | DSNU-40-80-PPV-A | 559308 | DSNU-40-80-PPS-A |
| | 100 | 195994 | DSNU-40-100-P-A | 196034 | DSNU-40-100-PPV-A | 559309 | DSNU-40-100-PPS-A |
| | 125 | 195995 | DSNU-40-125-P-A | 196035 | DSNU-40-125-PPV-A | 559310 | DSNU-40-125-PPS-A |
| | 150 | 5262536 | DSNU-40-150-P-A | 5262708 | DSNU-40-150-PPV-A | 5262772 | DSNU-40-150-PPS-A |
| | 160 | 195996 | DSNU-40-160-P-A | 196036 | DSNU-40-160-PPV-A | 559311 | DSNU-40-160-PPS-A |
| | 200 | 195997 | DSNU-40-200-P-A | 196037 | DSNU-40-200-PPV-A | 559312 | DSNU-40-200-PPS-A |
| | 250 | 195998 | DSNU-40-250-P-A | 196038 | DSNU-40-250-PPV-A | 559313 | DSNU-40-250-PPS-A |
| | 300 | 5262537 | DSNU-40-300-P-A | 5262709 | DSNU-40-300-PPV-A | 5262773 | DSNU-40-300-PPS-A |
| 320 | 195999 | DSNU-40-320-P-A | 196039 | DSNU-40-320-PPV-A | 559314 | DSNU-40-320-PPS-A | |

Datasheet

| Ordering data | | | | | | | |
|------------------|----------------|--|-----------------|---|-------------------|---|-------------------|
| Piston Ø [mm] | Stroke [mm] | P – Elastic cushioning rings/plates at both ends | | PPV – Pneumatic cushioning, adjustable at both ends | | PPS – Pneumatic cushioning, self-adjusting at both ends | |
| | | A – With position sensing | | A – With position sensing | | A – With position sensing | |
| | | Part no. | Type | Part no. | Type | Part no. | Type |
| 50 | 25 | 196000 | DSNU-50-25-P-A | 196040 | DSNU-50-25-PPV-A | 559315 | DSNU-50-25-PPS-A |
| | 40 | 196001 | DSNU-50-40-P-A | 196041 | DSNU-50-40-PPV-A | 559316 | DSNU-50-40-PPS-A |
| | 50 | 196002 | DSNU-50-50-P-A | 196042 | DSNU-50-50-PPV-A | 559317 | DSNU-50-50-PPS-A |
| | 80 | 196003 | DSNU-50-80-P-A | 196043 | DSNU-50-80-PPV-A | 559318 | DSNU-50-80-PPS-A |
| | 100 | 196004 | DSNU-50-100-P-A | 196044 | DSNU-50-100-PPV-A | 559319 | DSNU-50-100-PPS-A |
| | 125 | 196005 | DSNU-50-125-P-A | 196045 | DSNU-50-125-PPV-A | 559320 | DSNU-50-125-PPS-A |
| | 160 | 196006 | DSNU-50-160-P-A | 196046 | DSNU-50-160-PPV-A | 559321 | DSNU-50-160-PPS-A |
| | 200 | 196007 | DSNU-50-200-P-A | 196047 | DSNU-50-200-PPV-A | 559322 | DSNU-50-200-PPS-A |
| | 250 | 196008 | DSNU-50-250-P-A | 196048 | DSNU-50-250-PPV-A | 559323 | DSNU-50-250-PPS-A |
| 320 | 196009 | DSNU-50-320-P-A | 196049 | DSNU-50-320-PPV-A | 559324 | DSNU-50-320-PPS-A | |
| 63 | 25 | 196010 | DSNU-63-25-P-A | 196050 | DSNU-63-25-PPV-A | 559325 | DSNU-63-25-PPS-A |
| | 40 | 196011 | DSNU-63-40-P-A | 196051 | DSNU-63-40-PPV-A | 559326 | DSNU-63-40-PPS-A |
| | 50 | 196012 | DSNU-63-50-P-A | 196052 | DSNU-63-50-PPV-A | 559327 | DSNU-63-50-PPS-A |
| | 80 | 196013 | DSNU-63-80-P-A | 196053 | DSNU-63-80-PPV-A | 559328 | DSNU-63-80-PPS-A |
| | 100 | 196014 | DSNU-63-100-P-A | 196054 | DSNU-63-100-PPV-A | 559329 | DSNU-63-100-PPS-A |
| | 125 | 196015 | DSNU-63-125-P-A | 196055 | DSNU-63-125-PPV-A | 559330 | DSNU-63-125-PPS-A |
| | 160 | 196016 | DSNU-63-160-P-A | 196056 | DSNU-63-160-PPV-A | 559331 | DSNU-63-160-PPS-A |
| | 200 | 196017 | DSNU-63-200-P-A | 196057 | DSNU-63-200-PPV-A | 559332 | DSNU-63-200-PPS-A |
| | 250 | 196018 | DSNU-63-250-P-A | 196058 | DSNU-63-250-PPV-A | 559333 | DSNU-63-250-PPS-A |
| 320 | 196019 | DSNU-63-320-P-A | 196059 | DSNU-63-320-PPV-A | 559334 | DSNU-63-320-PPS-A | |

| Ordering data for variable strokes | | | | | | | |
|------------------------------------|----------------|--|-----------------|---|-------------------|---|------|
| Piston Ø [mm] | Stroke [mm] | P – Elastic cushioning rings/plates at both ends | | PPV – Pneumatic cushioning, adjustable at both ends | | PPS – Pneumatic cushioning, self-adjusting at both ends | |
| | | A – With position sensing | | A – With position sensing | | A – With position sensing | |
| | | Part no. | Type | Part no. | Type | Part no. | Type |
| 8 | 1 ... 100 | 14326 | DSNU-8-...-P-A | | | | |
| 10 | 1 ... 100 | 14325 | DSNU-10-...-P-A | | | | |
| 12 | 1 ... 200 | 14324 | DSNU-12-...-P-A | | | | |
| 16 | 1 ... 200 | 14323 | DSNU-16-...-P-A | | | | |
| 20 | 1 ... 320 | 14328 | DSNU-20-...-P-A | | | | |
| 25 | 1 ... 500 | 14327 | DSNU-25-...-P-A | | | | |
| | | | | | | | |
| | | | | 14320 | DSNU-16-...-PPV-A | | |
| | | | | 14321 | DSNU-20-...-PPV-A | | |
| | | | | 14322 | DSNU-25-...-PPV-A | | |

Ordering data – Modular product system

| Ordering table | | | | | | | | | |
|-----------------------------------|--|---------------|---------------|---------------|---|---------------|------------|--------------|------------|
| Size | 8 | 10 | 12 | 16 | 20 | 25 | Conditions | Code | Enter code |
| Module no. | 193986 | 193987 | 193988 | 193989 | 193990 | 193991 | | | |
| Function | Round cylinder, double-acting, based on ISO 6432 | | | | | | | DSNU | DSNU |
| Piston Ø [mm] | 8 | 10 | 12 | 16 | 20 | 25 | | -... | |
| Stroke [mm] | 1 ... 100 | | 1 ... 200 | | 1 ... 320 | 1 ... 500 | [1] | -... | |
| Cushioning | Elastic cushioning rings/plates at both ends | | | | | | | -P | |
| | - | | - | | Pneumatic cushioning, adjustable at both ends | | [2] | -PPV | |
| | - | | - | | Pneumatic cushioning, self-adjusting at both ends | | [3] | -PPS | |
| Position sensing | Via proximity switch | | | | | | [4] | -A | -A |
| Cylinder end cap | Lateral supply port, short end cap | | | | | | [5] | -MQ | |
| | Axial supply port, short end cap | | | | | | [5] | -MA | |
| | With mounting flange at front (direct mounting), bearing cap | | | | | | [6] | -MH | |
| Piston rod type | Through piston rod | | | | | | [7] | -S2 | |
| Stroke adjustment, advancing [mm] | 0 ... 15 | | - | | - | | [8] | -15KE | |
| | - | | 0 ... 25 | | - | | [9] | -25KE | |

- [1] -... Longer strokes on request
- [2] PPV Not with MA. In combination with S6, S10, L, A1 not with piston diameter 12 mm
- [3] PPS Not with MA, MH, S6, S10 and not with combination MQ-R3
- [4] A Minimum stroke > 10 mm required for reliable sensing
- [5] MQ, MA Not with S2, S10
- [6] MH Not with combination S6-R3.
Not with S10
- [7] S2 Not with S10
- [8] 15KE Not with MQ, MA, S2, S6, S10, L, A1, EX4
- [9] 25KE Not with MQ, MA, S2, S6, S10, L, A1, EX4
With piston Ø 20, 25: stroke only up to 250 mm

 - **Note**

The bellows kit DADB must not be used in combination with the variant MH.

The running characteristics change slightly when the bellows kit DADB is combined with the variant S10 or L

 - **Note**

Cylinders with position sensing require a minimum stroke of 10 mm to ensure reliable sensing.

Longer strokes on request

Ordering data – Modular product system

| Ordering table | | 8 | 10 | 12 | 16 | 20 | 25 | Conditions | Code | Enter code | |
|--------------------------------|------|----------------------------------|----|---|----|-----------|-----------|------------|----------|------------|--|
| Extended male thread | | Extended male piston rod thread | | | | | | | | | |
| | [mm] | 1 ... 15 | | 1 ... 20 | | 1 ... 25 | 1 ... 35 | [10] | -...K2 | | |
| Shortened male thread | | Shortened male piston rod thread | | | | | | | | | |
| | [mm] | 1 ... 4 | | | | 1 ... 8 | 1 ... 10 | [11] | -...K6 | | |
| Female thread | | Piston rod with female thread | | | | | | | | | |
| | | - | - | - | - | (M4) | (M6) | [12] | -K3 | | |
| Special thread | | Special piston rod thread | | | | | | | | | |
| | | - | - | - | - | - | M10 | | -“...”K5 | | |
| Extended piston rod at one end | | Piston rod extended at one end | | | | | | | | | |
| | [mm] | 1 ... 50 | | 1 ... 100 | | 1 ... 110 | 1 ... 150 | | ...K8 | | |
| Temperature resistance | | Heat-resistant seals max. 120 °C | | | | | | [13] | -S6 | | |
| Constant motion | | - | - | Slow speed (constant motion at low piston speeds) | | | | [14] | -S10 | | |
| Running characteristic | | Low friction | | | | | | [15] | -L | | |
| Corrosion protection | | - | - | High corrosion protection | | | | | -R3 | | |
| Wiper | | - | - | Increased chemical resistance | | | | [16] | -A1 | | |
| EU certification | | II 2GD | | | | | | [17] | -EX4 | | |

| | | |
|------|-----|----------------------------------|
| [10] | K2 | Not with K3, K6 |
| [11] | K6 | Not with K3 |
| [12] | K3 | Not with K5 |
| [13] | S6 | Not with S10 |
| [14] | S10 | Not with R3, L |
| [15] | L | Not with MQ, MA, MH, S2, S6, S10 |
| [16] | A1 | Not with MH, S6, S10, L |
| [17] | EX4 | Not with S6 |

Ordering data – Modular product system

| Ordering table | | | | | | | |
|------------------------------|---|---------------|---------------|---------------|------------|--------------|------------|
| Size | 32 | 40 | 50 | 63 | Conditions | Code | Enter code |
| Module no. | 193992 | 193993 | 193994 | 193995 | | | |
| Function | Double-acting round cylinder | | | | | DSNU | DSNU |
| Piston Ø [mm] | 32 | 40 | 50 | 63 | | -... | |
| Stroke [mm] | 1 ... 500 | | | | [1] | -... | |
| Cushioning | Elastic cushioning rings/plates at both ends | | | | | -P | |
| | Pneumatic cushioning, adjustable at both ends | | | | [2] | -PPV | |
| | Pneumatic cushioning, self-adjusting at both ends | | | | [3] | -PPS | |
| Position sensing | Via proximity switch | | | | [4] | -A | -A |
| Cylinder end cap | Lateral supply port, short end cap | | | | [5] | -MQ | |
| | Axial supply port, short end cap | | | | [6] | -MA | |
| | Mounting flange at the front (direct mounting), bearing cap | | | | [7] | -MH | |
| Piston rod type | Through piston rod | | | | [8] | -S2 | |
| Stroke adjustment, advancing | [mm] | 0 ... 25 | | | [9] | -25KE | |
| | [mm] | - | 0 ... 50 | | [10] | -50KE | |

- [1] -... Longer strokes on request
- [2] PPV Not with MA
- [3] PPS Not with MA, MH, S6, S10, combination MQ-R3 and R8
- [4] A Minimum stroke > 10 mm required for reliable sensing
- [5] MQ Not with S2, S10
- [6] MA Not with S2, S10 R8
- [7] MH Not with combination S6-R3.
Not with S10, R8
- [8] S2 Not with S10
- [9] 25KE Not with MQ, MA, S2, S6, S10, L, R8, A1, A6, EX4
- [10] 50KE Not with MQ, MA, S2, S6, S10, L, R8, A1, A6, EX4

 - **Note**

The bellows kit DADB must not be used in combination with the variant MH.

The running characteristics change slightly when the bellows kit DADB is combined with the variant S10 or L

 - **Note**

Cylinders with position sensing require a minimum stroke of 10 mm to ensure reliable sensing.

Longer strokes on request

Ordering data – Modular product system

| Ordering table | | | | | | | |
|--------------------------------|---|-----------|------|----------|------------|----------|------------|
| Size | 32 | 40 | 50 | 63 | Conditions | Code | Enter code |
| Extended male thread | Extended male piston rod thread | | | | | | |
| | [mm] | 1 ... 35 | | 1 ... 70 | [11] | -...K2 | |
| Shortened male thread | Shortened male piston rod thread | | | | | | |
| | [mm] | 1 ... 8 | | 1 ... 10 | [12] | -...K6 | |
| Female thread | Piston rod with female thread | | | | | | |
| | | (M6) | (M8) | (M10) | [13] | -K3 | |
| Special thread | Special piston rod thread | | | | | | |
| | | M10 | M12 | M16 | | -“...”K5 | |
| Extended piston rod at one end | Piston rod extended at one end | | | | | | |
| | [mm] | 1 ... 500 | | | | | ...K8 |
| Temperature resistance | Heat-resistant seals max. 120 °C | | | | [14] | -S6 | |
| Constant motion | Slow speed (constant motion at low piston speeds) | | | | [15] | -S10 | |
| Running characteristic | Low friction | | | | [16] | -L | |
| Corrosion protection | High corrosion protection | | | | [17] | -R3 | |
| Wiper | Dust protection | | | | [18] | -R8 | |
| | Increased chemical resistance | | | | [19] | -A1 | |
| | Metal wiper | | | | [20] | -A6 | |
| EU certification | II 2GD | | | | [21] | -EX4 | |

- [11] K2 Not with K3, K6
 [12] K6 Not with K3
 [13] K3 Not with K5
 [14] S6 Not with S10, S1
 [15] S10 Not with R3, R8, L
 [16] L Not with MQ, MA, MH, S2, S6, S10
 [17] R8 Not with MA, MH, S10, L, R3, A1, PPS
 [18] R3 Not with R8
 [19] A1 Not with MH, S6, S10, L, R8
 [20] A6 Not with S10, L, MH, P, PPS, S6, R3, EX4
 [21] EX4 Not with S6, S10

Ordering data – Modular product system

| Ordering table | | | | | | | | | | | |
|------------------------------|---|----------------|----------------|----------------|---|----------------|----------------|----------------|------------|--------------|------------|
| Size | 8 | 10 | 12 | 16 | 20 | 25 | 32 | 40 | Conditions | Code | Enter code |
| Module no. | 8150747 | 8149443 | 8149444 | 8149445 | 8149446 | 8149447 | 8149448 | 8149449 | | | |
| Function | Standards-based cylinder, double-acting, based on ISO 6432 | | | | | | | | | DSNU | DSNU |
| Piston Ø [mm] | 8 | 10 | 12 | 16 | 20 | 25 | 32 | 40 | | -... | |
| Stroke [mm] | 1 ... 100 | | 1 ... 200 | | 1 ... 320 | | 1 ... 500 | | [1] | -... | |
| Cushioning | Elastic cushioning rings/plates at both ends | | | | | | | | | -P | |
| | - | | - | | Pneumatic cushioning, adjustable at both ends | | | | | -PPV | |
| | - | | - | | Pneumatic cushioning, self-adjusting | | | | | -PPS | |
| Position sensing | Via proximity switch | | | | | | | | | -A | -A |
| Special material properties | Recommended for production facilities for manufacturing lithium-ion batteries | | | | | | | | [2] | -F1A | |
| Cylinder end cap | Standard | | | | | | | | | | |
| | Lateral supply port, short end cap | | | | | | | | | -MQ | |
| | Axial supply port, short end cap | | | | | | | | [3] | -MA | |
| Piston rod type | Piston rod at one end | | | | | | | | | | |
| | Through piston rod | | | | | | | | [4] | -S2 | |
| Stroke adjustment, advancing | [mm] | 0 ... 15 | | - | | | | | [5] | -15KE | |
| | [mm] | - | | 0 ... 25 | | | | | [6] | -25KE | |
| | [mm] | - | | | | | | 0 ... 50 | [7] | -50KE | |

- [1] -... Longer strokes on request
- [2] F1A With A only
- [3] MA Not with PPV, PPS
- [4] S2 Not with MQ, MA
- [5] 15KE Not with MQ, MA, S2
- [6] 25KE Not with MQ, MA, S2
- [7] 50KE Not with MQ, MA, S2

 **Note**

Cylinders with position sensing require a minimum stroke of 10 mm to ensure reliable sensing.
Longer strokes on request


Ordering data – Modular product system

| Ordering table | | | | | | | | | | | | |
|--------------------------------|----------------------------------|----------|-----------|-----------|-----------|-----------|------|------|------------|------|------------|----------|
| Size | 8 | 10 | 12 | 16 | 20 | 25 | 32 | 40 | Conditions | Code | Enter code | |
| Extended male thread | Extended male piston rod thread | | | | | | | | | | | |
| | [mm] | 1 ... 15 | 1 ... 20 | 1 ... 25 | 1 ... 35 | | | | | [8] | -...K2 | |
| Shortened male thread | Shortened male piston rod thread | | | | | | | | | | | |
| | [mm] | 1 ... 4 | 1 .. 8 | | | | | | | [9] | -...K6 | |
| Female thread | Piston rod with female thread | | | | | | | | | | | |
| | - | - | - | - | (M4) | (M6) | (M8) | | | | | -K3 |
| Special thread | Special piston rod thread | | | | | | | | | | | |
| | - | - | - | - | - | M10 | M12 | [10] | | | | -“...”K5 |
| Extended piston rod at one end | Piston rod extended at one end | | | | | | | | | | | |
| | [mm] | 1 ... 50 | 1 ... 100 | 1 ... 110 | 1 ... 150 | 1 ... 500 | | | | | -...K8 | |

- [8] K2 Not with K3
 [9] K6 Not with K2, K3
 [10] K5 Not with K3


Datasheet

P cushioning




-  - Diameter
8 ... 25 mm
ISO 6432

PPV cushioning



-  - Diameter
32 ... 63 mm

PPS cushioning



-  - Stroke length
1 ... 500 mm



- - Note

Additional measures are required for use in safety-related applications; in Europe, for example, the standards listed under the EC Machinery Directive must be observed.

Without additional measures in accordance with legally specified minimum requirements, the product is not suitable as a safety-oriented component in control systems.

General technical data

| Piston Ø | 8 | 10 | 12 | 16 | 20 | 25 | 32 | 40 | 50 | 63 | |
|--|--|----|-----------|-----|-----------|----------|-----------|----------|---------|---------|--|
| Based on standard | ISO 6432 | | | | | | - | | | | |
| Pneumatic connection | M5 | M5 | M5 | M5 | G1/8 | G1/8 | G1/8 | G1/4 | G1/4 | G3/8 | |
| Piston rod thread | M4 | M4 | M6 | M6 | M8 | M10x1.25 | M10x1.25 | M12x1.25 | M16x1.5 | M16x1.5 | |
| Stroke ¹⁾ [mm] | 1 ... 100 | | 1 ... 200 | | 1 ... 320 | | 1 ... 500 | | | | |
| Design | Piston/piston rod/cylinder barrel | | | | | | | | | | |
| Cushioning | Elastic cushioning rings/plates at both ends | | | | | | | | | | |
| DSNU...-P | Elastic cushioning rings/plates at both ends | | | | | | | | | | |
| DSNU...-PPV | Cushioning, adjustable at both ends | | | | | | | | | | |
| DSNU...-PPS | Cushioning, self-adjusting at both ends | | | | | | | | | | |
| Cushioning length | | | | | | | | | | | |
| DSNU...-PPV [mm] | - | | 9 | 12 | 15 | 17 | 14 | 18 | 20 | 21 | |
| DSNU...-PPS [mm] | - | | 12 | 15 | 17 | 14 | 18 | 20 | 21 | | |
| Position sensing | Via proximity switch | | | | | | | | | | |
| Type of mounting | With through-hole | | | | | | | | | | |
| | With accessories | | | | | | | | | | |
| Mounting position | Any | | | | | | | | | | |
| Holding force of the clamping unit [N] | 80 | 80 | 180 | 180 | 350 | 350 | 600 | 1000 | 1400 | 2000 | |
| Axial backlash under load [mm] | 0.2 | | 0.3 | | 0.5 | | 0.8 | | | | |
| Pneumatic connection on clamping unit | M5 | | | | | | | G1/8 | | | |

1) Cylinders with position sensing require a minimum stroke of 10 mm to ensure reliable sensing. Longer strokes on request.

Datasheet

| Operating and environmental conditions | |
|--|--|
| Operating medium | Compressed air to ISO 8573-1:2010 [7:4:4] |
| Note on the operating/ pilot medium | Lubricated operation possible (in which case lubricated operation will always be required) |
| Operating pressure ¹⁾ | [MPa] 0.3 ... 1 |
| | [bar] 3 ... 10 |
| Ambient temperature | [°C] -10 ... +80 |
| Corrosion resistance class CRC ²⁾ | |
| DSNU-... | 2 - Moderate corrosion stress |
| DSNU...-R3 | 3 - High corrosion stress |

1) With variant S2 (through piston rod) or variant KE (stroke adjustment), the minimum operating pressure may increase slightly after an idle period of > 24 hours.

2) More information www.festo.com/x/topic/crc

| Forces [N] and impact energy [J] | | | | | | | | | | |
|---|-------|-------|-------|------|------|------|------|------|------|------|
| Piston Ø | 8 | 10 | 12 | 16 | 20 | 25 | 32 | 40 | 50 | 63 |
| Theoretical force at 0.6 MPa (6 bar), advancing | 30 | 47 | 68 | 121 | 189 | 295 | 483 | 753 | 1178 | 1870 |
| Theoretical force at 0.6 MPa (6 bar), retracting | 23 | 40 | 51 | 104 | 158 | 247 | 415 | 633 | 990 | 1682 |
| Impact energy in the end positions for P cushioning ¹⁾ | | | | | | | | | | |
| DSNU-... | 0.03 | 0.05 | 0.07 | 0.15 | 0.2 | 0.3 | 0.4 | 0.7 | 1 | 1.3 |
| DSNU...-KE | 0.025 | 0.025 | 0.055 | 0.12 | 0.16 | 0.24 | 0.32 | 0.56 | 0.8 | 1 |

1) The values are reduced by approx. 50% at an ambient temperature of 80 °C

Permissible impact velocity:
$$V = \sqrt{\frac{2 \times E}{m_1 + m_2}}$$

Maximum permissible mass:
$$m_2 = \frac{2 \times E}{v^2} - m_1$$


V Perm. impact velocity
 E Max. impact energy
 m1 Moving mass (drive)
 m2 Moving payload

| Weight [g] | | | | | | | | | | | |
|------------------------------------|--------|-------|------|-------|-------|-----|-------|------|------|------|-----|
| Piston Ø | 8 | 10 | 12 | 16 | 20 | 25 | 32 | 40 | 50 | 63 | |
| DSNU-... | | | | | | | | | | | |
| Product weight with 0 mm stroke | 97.6 | 100.3 | 193 | 207.9 | 393.8 | 456 | 711.5 | 1287 | 2059 | 2556 | |
| Additional weight per 10 mm stroke | 2.4 | 2.7 | 4 | 4.6 | 7.2 | 11 | 15.5 | 24 | 40 | 44 | |
| Moving mass with 0 mm stroke | 7.5 | 8.5 | 18.5 | 23 | 44 | 71 | 121 | 230 | 413 | 459 | |
| Moving mass per 10 mm stroke | 1 | 1 | 2 | 2 | 4 | 6 | 9 | 16 | 25 | 25 | |
| DSNU...-S2 | | | | | | | | | | | |
| Moving mass with 0 mm stroke | 12 | 12.5 | 30 | 34.5 | 70 | 113 | 182 | 363 | 638 | 701 | |
| Moving mass per 10 mm stroke | 2 | 2 | 4 | 4 | 8 | 12 | 18 | 32 | 50 | 50 | |
| DSNU...-KE | | | | | | | | | | | |
| Moving mass with 0 mm stroke | [15KE] | 17 | 17.5 | - | - | - | - | - | - | - | |
| | [25KE] | - | - | 46 | 50.5 | 99 | 142 | 251 | 469 | 839 | 902 |
| | [50KE] | - | - | - | - | - | - | - | 491 | 918 | 981 |
| Moving mass per 10 mm stroke | 2 | 2 | 4 | 4 | 8 | 12 | 18 | 32 | 50 | 50 | |

Datasheet


Average piston speed v as a function of payload m in combination with cushioning PPS

Piston \varnothing 16




- DSNU-16-50
- ⋯ DSNU-16-100
- - - DSNU-16-200

Piston \varnothing 20




- DSNU-20-50
- ⋯ DSNU-20-100
- - - DSNU-20-200

Piston \varnothing 25




- DSNU-25-50
- ⋯ DSNU-25-100
- - - DSNU-25-200

Piston \varnothing 32




- DSNU-32-50
- ⋯ DSNU-32-100
- - - DSNU-32-200

Piston \varnothing 40



- DSNU-40-50
- ⋯ DSNU-40-100
- - - DSNU-40-200

Piston \varnothing 50



- DSNU-50-50
- ⋯ DSNU-50-100
- - - DSNU-50-200


Datasheet

Average piston speed v as a function of payload m in combination with cushioning PPS

Piston \varnothing 63

Note:


Average piston speed
= Stroke/movement time




- DSNU-63-50
- ⋯ DSNU-63-100
- - - DSNU-63-200

Engineering software for
P cushioning
PPV cushioning
PPS cushioning
→ <https://www.festo.com/x/pneumatic-sizing>


Max. transverse force F_q as a function of projection l



DSNU-...




- DSNU-8/10
- ⋯ DSNU-12/16
- - - DSNU-20
- · - · - DSNU-25




- · - · - DSNU-32
- - - DSNU-40
- DSNU-50/63

Datasheet


Max. transverse force F_q as a function of projection l



DSNU-...S2 – Through piston rod



- DSNU-8/10
- - - - DSNU-12/16
- - - - DSNU-20
- DSNU-25




- - - - DSNU-32
- - - - DSNU-40
- - - - DSNU-50/63

Datasheet

Materials

Sectional view



Round cylinder


| | | |
|-----|-------------------------------|----------------------------|
| [1] | Piston rod | |
| | DSNU-... | High-alloy steel |
| | DSNU-...-R3 | High-alloy stainless steel |
| [2] | Bearing cap | Anodised aluminium |
| [3] | Piston rod bearing | Sintered bronze |
| [4] | Housing, clamping unit | Wrought aluminium alloy |
| [5] | Clamping jaws | Brass |
| [6] | Cylinder barrel | High-alloy stainless steel |
| [7] | End cap | Anodised aluminium |
| [8] | Swivel bearing | Polymer |
| - | Piston, clamping unit | POM |
| | Spring | Spring steel |
| | Piston rod wiper seal | TPE-U(PU) |
| | Stroke adjustment DSNU-...-KE | |
| | Stop element | PE-UHMW |
| | Threaded coupling | Anodised aluminium |
| | LABS (PWIS) conformity | VDMA24364-B1/B2-L |
| | Cleanroom class | Class 6 to ISO 14644-1 |
| | Note on materials | RoHS-compliant |

Datasheet

Dimensions

Download CAD data → www.festo.com

DSNU-8 ... 25



Note
 Piston rod nut is not included in the scope of delivery for diameter 8 ... 20.
 + = plus stroke length

| ∅ [mm] | AM | B ∅ h8 | B2 | B3 | BE | BF | CD ∅ H9 | D ∅ | D4 ∅ | D6 ∅ | D7 ∅ | D8 |
|-----------|----|--------------|------|----|----------|----|---------------|--------|---------|---------|---------|----|
| 8 | 12 | 12 | 19.5 | 27 | M12x1.25 | 12 | 4 | 16 | 9.3 | 12 | 4.2 | M5 |
| 10 | | | | | | | | | 11.3 | | | |
| 12 | 16 | 16 | 24 | 32 | M16x1.5 | 17 | 6 | 20 | 13.3 | | | |
| 16 | | | | | | | | | 17.3 | | | |
| 20 | | | | | | | | | 21.3 | | | |
| 25 | 22 | 22 | 27 | 36 | M22x1.5 | 22 | 8 | 30 | 26.5 | 20 | | |

| ∅ [mm] | E1 | EE | EW | G | H1 | H2 | KK | KV | KW | MM ∅ | L | L2 |
|-----------|----|------|----|----|------|------|----------|----------|----|---------|----|------|
| 8 | M5 | M5 | 8 | 10 | 34.5 | 13.5 | M4 | 19 | 6 | 4 | 6 | 46 |
| 10 | | | 12 | | 41 | 16 | M6 | 24 | 8 | 6 | 9 | 50 |
| 12 | | | 16 | 16 | 16 | 62.5 | 18 | M8 | 32 | 11 | 8 | 12 |
| 16 | | 20 | 16 | 16 | 62.5 | 18 | M10x1.25 | 10 | | 10 | 12 | 69.5 |
| 25 | | G1/8 | 16 | 16 | 16 | 62.5 | 18 | M10x1.25 | 32 | 11 | 10 | 12 |

| ∅ [mm] | L6 | L7 | L8 | L9 | T3 | PL | VD | WF | XC | ZJ | ≈∅1 |
|-----------|----------|----|-----|----|----|-----|-------|------|-----|----|-----|
| 8 | 29 ±0.65 | 8 | - | - | 11 | 6 | 2 | ±1.2 | ±1 | 91 | - |
| 10 | | | - | - | | | | 16 | 93 | - | |
| 12 | 38 ±0.75 | 10 | - | 22 | | | | 113 | 110 | 5 | |
| 16 | 47 ±0.75 | 13 | - | 24 | | 120 | | 116 | 7 | | |
| 20 | 48 ±0.75 | | 4.5 | 20 | | 28 | | 142 | 139 | 9 | |
| 25 | 48 ±0.75 | 13 | 4.5 | 20 | 28 | 152 | 145.5 | 9 | | | |


Datasheet

Dimensions

DSNU-8 ... 25

S2 – Through piston rod

Download CAD data → www.festo.com



Note

The thread types at both piston rod ends are identical. The clamping unit is mounted at only one end.


In combination with variant Q (→ page 46) the right piston rod is square, the left piston rod round. The clamping unit is mounted on the left round piston rod.

In combination with variant K8 the piston rod extension is on the right piston rod only. The clamping unit is mounted on the left piston rod that is not extended.

+ = plus stroke length
++ = plus 2x stroke length

In combination with variant K8 and Q, the piston rod extension is on the right, square piston rod only.

KE – Stroke adjustment



+ = plus stroke length
++ = plus 2x stroke length


| ø [mm] | A5 | | D8 ø | ZJ | ZM | ≈ 2 | ≈ 3 |
|-----------|-------------------|-------|---------|-------|-------|-----|-----|
| | DSNU-... -15KE | -25KE | | | | | |
| 8 | 27.5 | - | 12 | 91 | 107 | 7 | 10 |
| 10 | | | | | | | |
| 12 | - | 43 | 15 | 110 | 132 | 10 | 13 |
| 16 | | | | 116 | 138 | | |
| 20 | | | | 139 | 163 | | |
| 25 | | 47 | 20 | 145.5 | 173.5 | 13 | 17 |

Datasheet

Dimensions

Download CAD data → www.festo.com

DSNU-32 ... 63



+ = plus stroke length

| ∅ [mm] | AM | B ∅ h9 | B2 | B3 | BE | BF | CD ∅ H9 | D ∅ | D1 ∅ | D4 ∅ | D6 ∅ | D7 ∅ |
|-----------|----|--------------|----|----|---------|----|---------------|--------|---------|---------|---------|---------|
| 32 | 22 | 30 | 30 | 46 | M30x1.5 | 26 | 10 | 41 | 42 | 33.6 | 20 | 4.4 |
| 40 | 24 | 38 | 36 | 56 | M38x1.5 | 30 | 12 | 49 | 50 | 41.6 | 24 | 6.8 |
| 50 | 32 | 45 | 50 | 65 | M45x1.5 | 33 | 16 | 57 | 60 | 52.4 | 30 | 8.5 |
| 63 | | | 54 | 72 | M45x1.5 | | | 70 | | 65.4 | 38 | |

| ∅ [mm] | D8 | E1 | EE | EW | G | H1 | H2 | KK | KW | MM ∅ f8 | L | L2 |
|-----------|-----|------|------|----|-------|-------|---------|----------|----|---------------|------|------|
| 32 | M5 | M5 | G1/8 | 16 | 19 | 67.5 | 23 | M10x1.25 | 8 | 12 | 13 | 69.5 |
| 40 | M8 | G1/8 | G1/4 | 18 | 25 | 89 | 28 | M12x1.25 | 10 | 16 | 15 | 84.6 |
| 50 | | G1/8 | | 21 | | 107.5 | 32.5 | 20 | | 16 | 86.2 | |
| 63 | M10 | G1/8 | G3/8 | 28 | 121.5 | 36 | M16x1.5 | 10 | 20 | 16 | 94.2 | |

| ∅ [mm] | L6 | L7 | L8 | L9 | T3 | PL | VD | WF | XC | ZJ | ⊖G1 |
|-----------|-------|------|----|----|----|----|----|----|-------|-------|-----|
| | ±0.75 | | | | | | | | ±1 | | |
| 32 | 55 | 12.5 | 5 | 15 | 12 | 9 | 2 | 34 | 172.5 | 158.5 | 10 |
| 40 | 69 | 17 | 7 | 20 | 18 | 12 | 3 | 39 | 208.6 | 192.6 | 13 |
| 50 | 78 | 20 | | 26 | 20 | | | 44 | 225.2 | 208.2 | 17 |
| 63 | 86 | 24 | 8 | 32 | 21 | 13 | | 45 | 242.2 | 225.2 | |


Datasheet

Dimensions

DSNU-32 ... 63

S2 – Through piston rod

Download CAD data → www.festo.com



Note

The thread types at both piston rod ends are identical. The clamping unit is mounted at only one end.


In combination with variant Q (→ page 46) the right piston rod is square, the left piston rod round. The clamping unit is mounted on the left round piston rod.

In combination with variant K8 the piston rod extension is on the right piston rod only. The clamping unit is mounted on the left piston rod that is not extended.

+ = plus stroke length
++ = plus 2x stroke length

In combination with variant K8 and Q, the piston rod extension is on the right, square piston rod only.

KE – Stroke adjustment



+ = plus stroke length
++ = plus 2x stroke length

| ∅ [mm] | A5 | | D8 ∅ | ZJ | ZM | ⊖ 2 | ⊖ 3 |
|-----------|-------------------|-------|---------|-------|-------|-----|-----|
| | DSNU-... -25KE | -50KE | | | | | |
| 32 | 52 | – | 30 | 158.5 | 192.5 | 17 | 24 |
| 40 | 56 | 81 | 35 | 192.6 | 231.6 | 19 | 30 |
| 50 | 67 | 92 | 45 | 208.2 | 252.2 | 24 | |
| 63 | | | | 225.2 | 270.2 | | |

Ordering data – Modular product system

| Ordering table | | | | | | | | | |
|-----------------------------------|--|---------------|---------------|---------------|---|---------------|------------|--------------|------------|
| Size | 8 | 10 | 12 | 16 | 20 | 25 | Conditions | Code | Enter code |
| Module no. | 193986 | 193987 | 193988 | 193989 | 193990 | 193991 | | | |
| Function | Round cylinder, double-acting, based on ISO 6432 | | | | | | | DSNU | DSNU |
| Piston Ø [mm] | 8 | 10 | 12 | 16 | 20 | 25 | | -... | |
| Stroke [mm] | 1 ... 100 | | 1 ... 200 | | 1 ... 320 | 1 ... 500 | [1] | -... | |
| Cushioning | Elastic cushioning rings/plates at both ends | | | | | | | -P | |
| | - | | - | | Pneumatic cushioning, adjustable at both ends | | [2] | -PPV | |
| | - | | - | | Pneumatic cushioning, self-adjusting at both ends | | [3] | -PPS | |
| Position sensing | Via proximity switch | | | | | | [4] | -A | -A |
| Cylinder end cap | Lateral supply port, short end cap | | | | | | [5] | -MQ | |
| | Axial supply port, short end cap | | | | | | [5] | -MA | |
| Piston rod type | Through piston rod | | | | | | | -S2 | |
| Stroke adjustment, advancing [mm] | 0 ... 15 | | - | | | | [6] | -15KE | |
| | - | | 0 ... 25 | | | | [7] | -25KE | |

- [1] -... Longer strokes on request
- [2] PPV Not with MA
- [3] PPS Not with MA, MH and not with combination MQ-R3
- [4] A Minimum stroke > 10 mm required for reliable sensing
- [5] MQ, MA Not with S2
- [6] 15KE Not with MQ, MA, S2
- [7] 25KE Not with MQ, MA, S2
With piston Ø 20, 25: stroke only up to 250 mm

 **Note**

Cylinders with position sensing require a minimum stroke of 10 mm to ensure reliable sensing.
Longer strokes on request

Ordering data – Modular product system

| Ordering table | | | | | | | | | |
|--------------------------------|----------------------------------|----------|-----------|----|-----------|-----------|------------|--------|------------|
| Size | 8 | 10 | 12 | 16 | 20 | 25 | Conditions | Code | Enter code |
| Extended male thread | Extended male piston rod thread | | | | | | | | |
| | [mm] | 1 ... 15 | 1 ... 20 | | 1 ... 25 | 1 ... 35 | [8] | -...K2 | |
| Shortened male thread | Shortened male piston rod thread | | | | | | | | |
| | [mm] | 1 ... 4 | | | 1 ... 8 | 1 ... 10 | [9] | -...K6 | |
| Female thread | Piston rod with female thread | | | | | | | | |
| | | - | - | - | - | (M4) | (M6) | [10] | -K3 |
| Special thread | Special piston rod thread | | | | | | | | |
| | | - | - | - | - | - | M10 | | -“...”K5 |
| Extended piston rod at one end | Piston rod extended at one end | | | | | | | | |
| | [mm] | 1 ... 50 | 1 ... 100 | | 1 ... 110 | 1 ... 150 | | ...K8 | |
| Clamping unit | Attached | | | | | | | | |
| | | | | | | | | -KP | -KP |

[8] K2 Not with K3, K6

[9] K6 Not with K3

[10] K3 Not with K5

Ordering data – Modular product system

| Ordering table | | | | | | | |
|------------------------------|---|---------------|---------------|---------------|------------|--------------|--------------|
| Size | 32 | 40 | 50 | 63 | Conditions | Code | Enter code |
| Module no. | 193992 | 193993 | 193994 | 193995 | | | |
| Function | Double-acting round cylinder | | | | | DSNU | DSNU |
| Piston Ø [mm] | 32 | 40 | 50 | 63 | | -... | |
| Stroke [mm] | 1 ... 500 | | | | [1] | -... | |
| Cushioning | Elastic cushioning rings/plates at both ends | | | | | -P | |
| | Pneumatic cushioning, adjustable at both ends | | | | [2] | -PPV | |
| | Pneumatic cushioning, self-adjusting at both ends | | | | [3] | -PPS | |
| Position sensing | Via proximity switch | | | | [4] | -A | -A |
| Cylinder end cap | Lateral supply port, short end cap | | | | [5] | -MQ | |
| | Axial supply port, short end cap | | | | [5] | -MA | |
| Piston rod type | Through piston rod | | | | | -S2 | |
| Stroke adjustment, advancing | [mm] | 0 ... 25 | | | [6] | -25KE | |
| | [mm] | - | 0 ... 50 | | | [7] | -50KE |

- [1] -... Longer strokes on request
- [2] PPV Not with MA
- [3] PPS Not with MA, MH and not with combination MQ-R3
- [4] A Minimum stroke > 10 mm required for reliable sensing
- [5] MQ, MA Not with S2
- [6] 25KE Not with MQ, MA, S2
With piston Ø 20, 25: stroke only up to 250 mm
- [7] 50KE Not with MQ, MA, S2

 **Note**

Cylinders with position sensing require a minimum stroke of 10 mm to ensure reliable sensing.
Longer strokes on request

Ordering data – Modular product system

| Ordering table | | | | | | | |
|--------------------------------|----------------------------------|-----------|------|----------|------------|----------|------------|
| Size | 32 | 40 | 50 | 63 | Conditions | Code | Enter code |
| Extended male thread | Extended male piston rod thread | | | | | | |
| | [mm] | 1 ... 35 | | 1 ... 70 | [8] | -...K2 | |
| Shortened male thread | Shortened male piston rod thread | | | | | | |
| | [mm] | 1 ... 8 | | 1 ... 10 | [9] | -...K6 | |
| Female thread | Piston rod with female thread | | | | | | |
| | | (M6) | (M8) | (M10) | [10] | -K3 | |
| Special thread | Special piston rod thread | | | | | | |
| | | M10 | M12 | M16 | | -“...”K5 | |
| Extended piston rod at one end | Piston rod extended at one end | | | | | | |
| | [mm] | 1 ... 500 | | | | ...K8 | |
| Clamping unit | Attached | | | | | -KP | -KP |

[8] K2 Not with K3, K6


[9] K6 Not with K3

[10] K3 Not with K5

Round cylinders DSNU-Q, protected against rotation


Datasheet

P cushioning



-  Diameter
12 ... 25 mm
ISO 6432

PPV cushioning



-  Diameter
32 ... 63 mm
-  Stroke length
1 ... 500 mm



| General technical data | | 12 | 16 | 20 | 25 | 32 | 40 | 50 | 63 |
|-------------------------------|--|---|------|-----------|-----------|--|-----------|---------|-----------|
| Piston Ø | | 12 | 16 | 20 | 25 | 32 | 40 | 50 | 63 |
| Based on standard | | ISO 6432 | | | | - | | | |
| Pneumatic connection | | M5 | M5 | G1/8 | G1/8 | G1/8 | G1/4 | G1/4 | G3/8 |
| Piston rod thread | | M6 | M6 | M8 | M10x1.25 | M10x1.25 | M12x1.25 | M16x1.5 | M16x1.5 |
| Stroke ¹⁾ | [mm] | 1 ... 160 | | 1 ... 200 | 1 ... 250 | 1 ... 300 | 1 ... 400 | | 1 ... 500 |
| Design | | Piston Protected against rotation with square piston rod | | | | | | | |
| Max. torque at the piston rod | [Nm] | 0.10 | 0.10 | 0.20 | 0.45 | 0.8 | 1.1 | 1.5 | 1.5 |
| Cushioning | | | | | | | | | |
| DSNU-...-P | Elastic cushioning rings/plates at both ends | - | | | | Elastic cushioning rings/plates at both ends | | | |
| DSNU-...-PPV | | Pneumatic cushioning adjustable at both ends | | | | | | | |
| Cushioning length (PPV) | [mm] | - | 12 | 15 | 17 | 14 | 18 | 20 | 21 |
| Position sensing | | Via proximity switch | | | | | | | |
| Type of mounting | | With accessories | | | | | | | |
| Mounting position | | Any | | | | | | | |

- 1) Cylinders with position sensing require a minimum stroke of 10 mm to ensure reliable sensing.
Longer strokes on request.

| Operating and environmental conditions | | 12 | 16 | 20 | 25 | 32 | 40 | 50 | 63 |
|--|-------|--|----|-----------|----|-------------|----|----|----|
| Operating medium | | Compressed air to ISO 8573-1:2010 [7:4:4] | | | | | | | |
| Note on the operating/pilot medium | | Lubricated operation possible (in which case lubricated operation will always be required) | | | | | | | |
| Operating pressure ¹⁾ | | | | | | | | | |
| DSNU-... | [MPa] | 0.15 ... 1 ²⁾ | | 0.1 ... 1 | | | | | |
| | [bar] | 1.5 ... 10 ²⁾ | | 1 ... 10 | | | | | |
| DSNU-Q-...-S6 | [MPa] | - | | | | 0.1 ... 0.8 | | | |
| | [bar] | - | | | | 1 ... 8 | | | |
| Ambient temperature ³⁾ | | | | | | | | | |
| DSNU-... | [°C] | -20 ... +80 | | | | | | | |
| DSNU-Q-...-S6 | [°C] | - | | | | 0 ... +120 | | | |
| Corrosion resistance class CRC ⁴⁾ | | | | | | | | | |
| DSNU-... | | 2 - Moderate corrosion stress | | | | | | | |
| DSNU-Q-...-R3 | | 3 - High corrosion stress | | | | | | | |

- 1) With variant S2 (through piston rod) or variant KE (stroke adjustment), the minimum operating pressure may increase slightly after an idle period of > 24 hours.
2) For DSNU-12-...-Q-PPV (pneumatic cushioning adjustable at both ends): 0.2 ... 1 MPa (2 ... 10 bar)
3) Note operating range of proximity switches
4) More information www.festo.com/x/topic/crc

Datasheet

| ATEX ¹⁾ | |
|---|---|
| ATEX category for gas | II 2G |
| Type of (ignition) protection for gas | c T4 |
| ATEX category for dust | II 2D |
| Type of ignition protection for dust | c 120 °C |
| Explosion-proof ambient temperature | -20 °C ≤ Ta ≤ +60 °C |
| CE marking (see declaration of conformity) | To EU Explosion Protection Directive (ATEX) |
| UKCA marking (see declaration of conformity) | To UK explosion regulations |
| Explosion protection certification outside the EU | EPL Db (GB) |
| | EPL Gb (GB) |

1) Note the ATEX certification of the accessories.

| Forces [N] and impact energy [J] | | | | | | | | |
|---|-------|-------|------|------|------|------|------|------|
| Piston Ø | 12 | 16 | 20 | 25 | 32 | 40 | 50 | 63 |
| Theoretical force at 0.6 MPa (6 bar), advancing | 68 | 121 | 189 | 295 | 483 | 753 | 1178 | 1870 |
| Theoretical force at 0.6 MPa (6 bar), retracting | 51 | 104 | 158 | 247 | 415 | 633 | 990 | 1682 |
| Impact energy in the end positions for P cushioning ¹⁾ | | | | | | | | |
| DSNU-... | 0.07 | 0.15 | 0.2 | 0.3 | 0.4 | 0.7 | 1 | 1.3 |
| DSNU-...-S6 | 0.035 | 0.075 | 0.1 | 0.15 | 0.2 | 0.35 | 0.5 | 0.65 |
| DSNU-...-KE | 0.055 | 0.12 | 0.16 | 0.24 | 0.32 | 0.56 | 0.8 | 1 |

1) The values are reduced by approx. 50% at an ambient temperature of 80 °C

Permissible impact velocity:
$$V = \sqrt{\frac{2 \times E}{m_1 + m_2}}$$

Maximum permissible mass:
$$m_2 = \frac{2 \times E}{v^2} - m_1$$


V Perm. impact velocity
 E Max. impact energy
 m1 Moving mass (drive)
 m2 Moving payload

| Weight [g] | | | | | | | | |
|------------------------------------|--------|------|------|-----|-------|-----|------|------|
| Piston Ø | 12 | 16 | 20 | 25 | 32 | 40 | 50 | 63 |
| DSNU-... | | | | | | | | |
| Product weight with 0 mm stroke | 80 | 110 | 215 | 275 | 370.5 | 661 | 1087 | 1445 |
| Additional weight per 10 mm stroke | 4 | 4.6 | 7.2 | 11 | 15.5 | 24 | 40 | 44 |
| Moving mass with 0 mm stroke | 18.5 | 23 | 44 | 71 | 121 | 230 | 413 | 459 |
| Moving mass per 10 mm stroke | 2 | 2 | 4 | 6 | 9 | 16 | 25 | 25 |
| DSNU-...-S2 | | | | | | | | |
| Moving mass with 0 mm stroke | 30 | 34.5 | 70 | 113 | 182 | 363 | 638 | 701 |
| Moving mass per 10 mm stroke | 4 | 4 | 8 | 12 | 18 | 32 | 50 | 50 |
| DSNU-...-KE | | | | | | | | |
| Moving mass with 0 mm stroke | [15KE] | - | - | - | - | - | - | - |
| | [25KE] | 46 | 50.5 | 99 | 142 | 251 | 469 | 839 |
| | [50KE] | - | - | - | - | - | 491 | 918 |
| Moving mass per 10 mm stroke | 4 | 4 | 8 | 12 | 18 | 32 | 50 | 50 |

Datasheet

Materials

Sectional view



Datasheet


| Round cylinder | |
|----------------|-------------------------------|
| [1] | Piston rod |
| | DSNU-... |
| | High-alloy steel |
| | DSNU-...-R3 |
| | High-alloy stainless steel |
| [2] | Piston rod bearing |
| | Sintered bronze |
| [3] | Bearing cap |
| | Anodised aluminium |
| [4] | Cylinder barrel |
| | High-alloy stainless steel |
| [5] | End cap |
| | Anodised aluminium |
| [6] | Swivel bearing |
| | Polymer |
| - | Piston rod wiper seal |
| | TPE-U(PU) |
| | Stroke adjustment DSNU-...-KE |
| | Stop element |
| | PE-UHMW |
| | Threaded coupling |
| | Aluminium |
| | LABS (PWIS) conformity |
| | VDMA24364-B1/B2-L |
| | Cleanroom class |
| | Class 6 to ISO 14644-1 |
| | Note on materials |
| | RoHS-compliant |

Datasheet

Dimensions

Download CAD data → www.festo.com

DSNU-12 ... 25



- - **Note**
 Piston rod nut is not included in the scope of delivery for diameter 12 ... 20.
 + = plus stroke length

| ∅ | AM | B ∅ h8 | B1 | BE | BF | CD ∅ H9 | D ∅ | D4 ∅ | E | EE | EW |
|----|----|--------------|-----|---------|----|---------------|--------|---------|----|------|----|
| 12 | 16 | 16 | 5.5 | M16x1.5 | 17 | 6 | 20 | 13.3 | 18 | M5 | 12 |
| 16 | | | | | | | | 17.3 | | | |
| 20 | 20 | 22 | 7 | M22x1.5 | 20 | 8 | 30 | 21.3 | 26 | G1/8 | 16 |
| 25 | 22 | | 9 | | 22 | | | 26.5 | | | |


| ∅ | G | KK | KV | KW | L | L2 | PL | VD | WF ±1.2 | XC ±1 | ZJ |
|----|----|----------|----|----|----|------|-----|----|------------|----------|----|
| 12 | 10 | M6 | 24 | 8 | 9 | 50 | 6 | 2 | 22 | 75 | 72 |
| 16 | | | | | | 56 | | | | | |
| 20 | 16 | M8 | 32 | 11 | 12 | 68 | 8.2 | 24 | 95 | 92 | |
| 25 | | M10x1.25 | | | | 69.5 | | | | | 28 |

Datasheet

Dimensions

Download CAD data → www.festo.com

S2 – Through piston rod




Note

The thread types at both piston rod ends are identical. The clamping unit is mounted at only one end. In combination with variant Q, the right piston rod is square, the left piston rod round. The clamping unit is mounted on the left round piston rod.

+ = plus stroke length
 ++ = plus 2x stroke length

KE – Stroke adjustment



+ = plus stroke length
 ++ = plus 2x stroke length


| ø [mm] | A5 | | D8 ø | ZJ | ZM | √Ra 2 | √Ra 3 |
|-----------|-------------------|-------|---------|-------|-----|-------|-------|
| | DSNU-... -15KE | -25KE | | | | | |
| 12 | - | 43 | 15 | 110 | 132 | 10 | 13 |
| 16 | | | | 116 | 138 | | |
| 20 | | 47 | 20 | 139 | 163 | | |
| 25 | 145.5 | | | 173.5 | | | |

Datasheet

Dimensions

Download CAD data → www.festo.com

DSNU-32 ... 63



| ∅ | AM | B ∅ h8 | B1 | BE | BF | CD ∅ H9 | D ∅ | D1 ∅ | D4 ∅ | E | EE | EW |
|----|----|--------------|----|---------|----|---------------|--------|---------|---------|----|------|----|
| 32 | 22 | 30 | 10 | M30x1.5 | 26 | 10 | 41 | 42 | 33.6 | 38 | G1/8 | 16 |
| 40 | 24 | 38 | 12 | M38x1.5 | 30 | 12 | 49 | 50 | 41.6 | 45 | G1/4 | 18 |
| 50 | 32 | 45 | 16 | M45x1.5 | 33 | 16 | 57 | 60 | 52.4 | – | G1/4 | 21 |
| 63 | 32 | 45 | 16 | M45x1.5 | 33 | 16 | 70 | 60 | 65.4 | – | G3/8 | 21 |


| ∅ | G | KK | KW | L | L2 | PL | VD | WF ±1.2 | XC ±1 | ZJ |
|----|----|----------|----|----|------|----|----|------------|----------|-------|
| 32 | 19 | M10x1.25 | 8 | 13 | 69.5 | 9 | 2 | 34 | 117.5 | 103.5 |
| 40 | 25 | M12x1.25 | 10 | 15 | 84.6 | 12 | 3 | 39 | 139.6 | 123.6 |
| 50 | 25 | M16x1.5 | 10 | 16 | 86.2 | 12 | 3 | 44 | 147.2 | 130.2 |
| 63 | 28 | M16x1.5 | 10 | 16 | 94.2 | 13 | 3 | 45 | 156.2 | 139.2 |

Datasheet

Dimensions

Download CAD data → www.festo.com

S2 – Through piston rod




Note

The thread types at both piston rod ends are identical. The clamping unit is mounted at only one end. In combination with variant Q, the right piston rod is square, the left piston rod round. The clamping unit is mounted on the left round piston rod.

+ = plus stroke length
++ = plus 2x stroke length

KE – Stroke adjustment



+ = plus stroke length
++ = plus 2x stroke length

| ∅ [mm] | A5 | | D8 ∅ | ZJ | ZM | ⊖ 2 | ⊖ 3 |
|-----------|-------------------|-------|---------|-------|-------|-----|-----|
| | DSNU-... -25KE | -50KE | | | | | |
| 32 | 52 | – | 30 | 158.5 | 192.5 | 17 | 24 |
| 40 | 56 | 81 | 35 | 192.6 | 231.6 | 19 | 30 |
| 50 | 67 | 92 | 45 | 208.2 | 252.2 | 24 | |
| 63 | | | | 225.2 | 270.2 | | |

Ordering data – Modular product system

| Ordering table | | | | | | | |
|-----------------------------------|--|--|---------------|---------------|------------|--------------|------------|
| Size | 12 | 16 | 20 | 25 | Conditions | Code | Enter code |
| Module no. | 193988 | 193989 | 193990 | 193991 | | | |
| Function | Round cylinder, double-acting, based on ISO 6432 | | | | | DSNU | DSNU |
| Piston Ø [mm] | 12 | 16 | 20 | 25 | | -... | |
| Stroke [mm] | 1 ... 160 | | 1 ... 200 | 1 ... 250 | [1] | -... | |
| Cushioning | Elastic cushioning rings/plates at both ends | - | - | - | | -P | |
| | - | Pneumatic cushioning, adjustable at both ends | | | [2] | -PPV | |
| Position sensing | Via proximity switch | | | | [3] | -A | -A |
| Cylinder end cap | Lateral supply port, short end cap | | | | [4] | -MQ | |
| | Axial supply port, short end cap | - | - | - | [4] | -MA | |
| | - | With mounting flange at front (direct mounting), bearing cap | | | [5] | -MH | |
| Protection against rotation | Square piston rod | | | | | -Q | -Q |
| Piston rod type | Through piston rod | | | | | -S2 | |
| Stroke adjustment, advancing [mm] | 0 ... 25 | | | | [6] | -25KE | |

- [1] -... Longer strokes on request
 [2] PPV Not with MA
 [3] A Minimum stroke > 10 mm required for reliable sensing
 [4] MQ, MA Not with S2
 [5] MH Not with combination Q-R3
 [6] 25KE Not with MQ, MA, S2, EX4
 With piston Ø 20, 25: stroke only up to 250 mm

 - **Note**
 The bellows kit DADB must not be used in combination with the variant Q.

 - **Note**
 Cylinders with position sensing require a minimum stroke of 10 mm to ensure reliable sensing.
 Longer strokes on request

Ordering data – Modular product system

| Ordering table | | | | | | | |
|--------------------------------|----------------------------------|-----------|---------------------------|-----------|------------|----------|------------|
| Size | 12 | 16 | 20 | 25 | Conditions | Code | Enter code |
| Extended male thread | Extended male piston rod thread | | | | | | |
| | [mm] | 1 ... 20 | 1 ... 25 | 1 ... 35 | [7] | -...K2 | |
| Shortened male thread | Shortened male piston rod thread | | | | | | |
| | [mm] | 1 ... 4 | 1 ... 8 | 1 ... 10 | [8] | -...K6 | |
| Female thread | Piston rod with female thread | | | | | | |
| | | | (M4) | (M6) | [9] | -K3 | |
| Special thread | Special piston rod thread | | | | | | |
| | | | | M10 | | -“...”K5 | |
| Extended piston rod at one end | Piston rod extended at one end | | | | | | |
| | [mm] | 1 ... 100 | 1 ... 110 | 1 ... 150 | | ...K8 | |
| Clamping unit | Attached | | | | [10] | -KP | |
| Corrosion protection | - | | High corrosion protection | | | | -R3 |
| EU certification | II 2GD | | | | [11] | -EX4 | |

- [7] K2 Not with K3, K6
 [8] K6 Not with K3
 [9] K3 Not with K5
 [10] KP Only with S2. Not with R3
 [11] EX4 Not with KP

Ordering data – Modular product system

| Ordering table | | | | | | | |
|------------------------------|---|---------------|---------------|---------------|------------|--------------|------------|
| Size | 32 | 40 | 50 | 63 | Conditions | Code | Enter code |
| Module no. | 193992 | 193993 | 193994 | 193995 | | | |
| Function | Double-acting round cylinder | | | | | DSNU | DSNU |
| Piston Ø [mm] | 32 | 40 | 50 | 63 | | -... | |
| Stroke [mm] | 1 ... 300 | 1 ... 400 | | 1 ... 500 | [1] | -... | |
| Cushioning | Elastic cushioning rings/plates at both ends | | | | | -P | |
| | Pneumatic cushioning adjustable at both ends | | | | [2] | -PPV | |
| Position sensing | Via proximity switch | | | | [3] | -A | -A |
| Cylinder end cap | Lateral supply port, short end cap | | | | [4] | -MQ | |
| | Axial supply port, short end cap | | | | [4] | -MA | |
| | Mounting flange at the front (direct mounting), bearing cap | | | | [5] | -MH | |
| Protection against rotation | Square piston rod | | | | | -Q | -Q |
| Piston rod type | Through piston rod | | | | | -S2 | |
| Stroke adjustment, advancing | [mm] | 0 ... 25 | | | [6] | -25KE | |
| | [mm] | - | 0 ... 50 | | [6] | -50KE | |

- [1] -... Longer strokes on request
- [2] PPV Not with MA
- [3] A Minimum stroke > 10 mm required for reliable sensing
- [4] MQ, MA Not with S2
- [5] MH Not with combinations: Q-R3, S6-R3. Not with KP
- [6] KE Not with MQ, MA, S2, S6, EX4



Note

The bellows kit DADB must not be used in combination with the variant Q.



Note

Cylinders with position sensing require a minimum stroke of 10 mm to ensure reliable sensing.
Longer strokes on request

Ordering data – Modular product system

| Ordering table | | | | | | | |
|--------------------------------|----------------------------------|-----------|------|----------|------------|------|------------|
| Size | 32 | 40 | 50 | 63 | Conditions | Code | Enter code |
| Extended male thread | Extended male piston rod thread | | | | | | |
| | [mm] | 1 ... 35 | | 1 ... 70 | | [7] | -...K2 |
| Shortened male thread | Shortened male piston rod thread | | | | | | |
| | [mm] | 1 ... 8 | | 1 ... 10 | | [8] | -...K6 |
| Female thread | Piston rod with female thread | | | | | | |
| | | (M6) | (M8) | (M10) | | [9] | -K3 |
| Special thread | Special piston rod thread | | | | | | |
| | | M10 | M12 | M16 | | | -“...”K5 |
| Extended piston rod at one end | Piston rod extended at one end | | | | | | |
| | [mm] | 1 ... 500 | | | | | |
| Clamping unit | Attached | | | | | [10] | -KP |
| Temperature resistance | Heat-resistant seals max. 120 °C | | | | | | -S6 |
| Corrosion protection | High corrosion protection | | | | | | -R3 |
| EU certification | II 2GD | | | | | [11] | -EX4 |

- [7] K2 Not with K3, K6
 [8] K6 Not with K
 [9] K3 Not with K5
 [10] KP Only with S2. Not with S6, R3
 [11] EX4 Not with KP, S6

Accessories

Foot mounting HBN/CRHBN

Scope of delivery:

HBN/CRHBN-...x1: 1 foot


HBN/CRHBN-...x2: 2 feet and 1 nut

Material:

HBN: Galvanised steel

CRHBN: High-alloy stainless steel

RoHS-compliant



+ = plus stroke length

| For Ø [mm] | AB Ø | AH | AO | AT | AU | R1 | SA | | TR | US | XA | | XS | |
|---------------|---------|----|----|----|----|----|-------|---------|----|----|-------|---------|----|---------|
| | | | | | | | | DSNU-KP | | | | DSNU-KP | | DSNU-KP |
| 8, 10 | 4.5 | 16 | 5 | 3 | 11 | 10 | 68 | 97 | 25 | 35 | 73 | 102 | 24 | - |
| 12 | 5.5 | 20 | 6 | 4 | 14 | 13 | 78 | 116 | 32 | 42 | 86 | 124 | 32 | - |
| 16 | 5.5 | 20 | 6 | 4 | 14 | 13 | 84 | 122 | 32 | 42 | 92 | 130 | 32 | - |
| 20 | 6.6 | 25 | 8 | 5 | 17 | 20 | 102 | 149 | 40 | 54 | 109 | 156 | 36 | - |
| 25 | 6.6 | 25 | 8 | 5 | 17 | 20 | 103.5 | 151.5 | 40 | 54 | 114.5 | 162.5 | 40 | - |


| For Ø [mm] | Basic version | | | | High corrosion protection | | | |
|---------------|-------------------|------------|----------|-------------|---------------------------|------------|----------|---------------|
| | CRC ¹⁾ | Weight [g] | Part no. | Type | CRC ¹⁾ | Weight [g] | Part no. | Type |
| 8, 10 | 1 | 22 | 5123 | HBN-8/10x1 | - | - | - | |
| | 1 | 54 | 5124 | HBN-8/10x2 | - | - | - | |
| 12, 16 | 1 | 43 | 5125 | HBN-12/16x1 | 4 | 43 | 161866 | CRHBN-12/16x1 |
| | 1 | 107 | 5126 | HBN-12/16x2 | 4 | 107 | 162999 | CRHBN-12/16x2 |
| 20, 25 | 1 | 95 | 5127 | HBN-20/25x1 | 4 | 94 | 161867 | CRHBN-20/25x1 |
| | 1 | 237 | 5128 | HBN-20/25x2 | 4 | 236 | 162998 | CRHBN-20/25x2 |

1) More information www.festo.com/x/topic/crc

Accessories

Foot mounting HBN/CRH

Material:
 HBN: Galvanised steel
 CRH: High-alloy stainless steel
 RoHS-compliant



Dimensions and ordering data

| For Ø [mm] | AB Ø | AH | AO | AT | AU | SA | | TR | US | XA | | XS | |
|---------------|---------|----|----|----|----|-------|---------|----|----|-------|---------|----|---|
| | | | | | | | DSNU-KP | | | | DSNU-KP | | |
| 32 | 7 | 28 | 7 | 4 | 14 | 97.5 | 151 | 52 | 66 | 117.5 | 171 | 44 | - |
| 40 | 9 | 33 | 10 | 5 | 20 | 124.6 | 192.1 | 60 | 80 | 143.6 | 206.1 | 54 | - |
| 50 | 9 | 40 | 10 | 6 | 20 | 126.2 | 202.7 | 70 | 90 | 150.2 | 226.7 | 58 | - |
| 63 | 9 | 45 | 10 | 6 | 20 | 134.2 | 218.7 | 76 | 96 | 159.2 | 243.7 | 59 | - |


| For Ø [mm] | Basic version | | | | High corrosion protection | | | |
|---------------|-------------------|------------|---------------|-----------------|---------------------------|------------|---------------|---------------|
| | CRC ¹⁾ | Weight [g] | Part no. | Type | CRC ¹⁾ | Weight [g] | Part no. | Type |
| 32 | 1 | 353 | 195851 | HBN-32x2 | 4 | 353 | 162951 | CRH-32 |
| 40 | 1 | 611 | 195852 | HBN-40x2 | 4 | 611 | 162952 | CRH-40 |
| 50 | 1 | 916 | 195853 | HBN-50x2 | 4 | 916 | 162953 | CRH-50 |
| 63 | 1 | 1066 | 195854 | HBN-63x2 | 4 | 1066 | 162954 | CRH-63 |

1) More information www.festo.com/x/topic/crc

Accessories

Flange mounting FBN/CRFBN

Material:
 FBN: Galvanised steel
 CRFBN: High-alloy stainless steel



Dimensions and ordering data

| For Ø [mm] | AB Ø | AT | TF | UF | UR | W | ZF | |
|---------------|---------|----|----|----|----|----|-------|---------|
| | | | | | | | | DSNU-KP |
| 8, 10 | 4.5 | 3 | 30 | 40 | 25 | 13 | 65 | 94 |
| 12 | 5.5 | 4 | 40 | 53 | 30 | 18 | 76 | 114 |
| 16 | 5.5 | 4 | 40 | 53 | 30 | 18 | 82 | 120 |
| 20 | 6.6 | 5 | 50 | 66 | 40 | 19 | 97 | 144 |
| 25 | 6.6 | 5 | 50 | 66 | 40 | 23 | 102.5 | 150.5 |

| For Ø [mm] | Basic version | | | | High corrosion protection | | | |
|---------------|-------------------|------------|-------------|------------------|---------------------------|------------|---------------|--------------------|
| | CRC ¹⁾ | Weight [g] | Part no. | Type | CRC ¹⁾ | Weight [g] | Part no. | Type |
| 8, 10 | 1 | 12 | 5129 | FBN-8/10 | - | - | - | - |
| 12, 16 | 1 | 26 | 5130 | FBN-12/16 | 4 | 26 | 161864 | CRFBN-12/16 |
| 20, 25 | 1 | 52 | 5131 | FBN-20/25 | 4 | 52 | 161865 | CRFBN-20/25 |

1) More information www.festo.com/x/topic/crc

Accessories


Flange mounting FBN/CRFV

Material:

FBN: Galvanised steel

CRFV: High-alloy stainless steel

RoHS-compliant



Dimensions and ordering data

| For Ø [mm] | AB Ø | AT | H1 | TF | TR | US | W ±1.2 | ZF | |
|---------------|---------|----|----|----|----|----|-----------|-------|---------|
| | | | | | | | | | DSNU-KP |
| 32 | 7 | 4 | 14 | 28 | 52 | 66 | 30 | 107.5 | 161 |
| 40 | 9 | 5 | 18 | 30 | 60 | 80 | 29 | 128.6 | 191.1 |
| 50 | 9 | 6 | 20 | 40 | 70 | 90 | 38 | 136.2 | 212.6 |
| 63 | 9 | 6 | 20 | 50 | 76 | 96 | 39 | 145.2 | 229.7 |


| For Ø [mm] | Basic version | | | | High corrosion protection | | | |
|---------------|-------------------|------------|----------|--------|---------------------------|------------|----------|---------|
| | CRC ¹⁾ | Weight [g] | Part no. | Type | CRC ¹⁾ | Weight [g] | Part no. | Type |
| 32 | 1 | 103 | 195855 | FBN-32 | 4 | 103 | 161858 | CRFV-32 |
| 40 | 1 | 191 | 195856 | FBN-40 | 4 | 191 | 161859 | CRFV-40 |
| 50 | 1 | 292 | 195857 | FBN-50 | 4 | 292 | 161860 | CRFV-50 |
| 63 | 1 | 367 | 195858 | FBN-63 | 4 | 367 | 161861 | CRFV-63 |

1) More information www.festo.com/x/topic/crc

Accessories

Swivel mounting SBN

Material:
 Retaining ring: Anodised wrought aluminium alloy
 Bearing: Bronze
 Screws: Galvanised steel
 Bracket: Steel
 Cannot be used on the bearing cap in combination with bellows kit DADB.




Dimensions and ordering data

| For Ø | CM | FL | GL | HB | L1 | LE | MR | RF | RG | UK | UX | CRC ¹⁾ | Weight | Part no. | Type |
|-------|----------|----|----|----|-------|----|----|----|----|------|----|-------------------|--------|----------|-----------|
| [mm] | | | | | max. | | | | | | | | [g] | | |
| 20/25 | 38.1±0.4 | 35 | 20 | 7 | 60.2 | 31 | 12 | 20 | 24 | 46.1 | 40 | 1 | 238 | 539927 | SBN-20/25 |
| 32 | 46.1±0.2 | 40 | 27 | 9 | 72.2 | 35 | 13 | 28 | 30 | 56.1 | 50 | 1 | 361 | 539924 | SBN-32 |
| 40 | 57.1±0.2 | 45 | 30 | 9 | 88.2 | 39 | 14 | 36 | 34 | 69.1 | 54 | 1 | 593 | 539925 | SBN-40 |
| 50/63 | 70.1±0.4 | 50 | 34 | 9 | 102.2 | 44 | 16 | 42 | 35 | 82.1 | 65 | 1 | 894 | 539926 | SBN-50/63 |

1) More information www.festo.com/x/topic/crc

Swivel mounting WBN

Material:
 Galvanised steel
 RoHS-compliant
 Cannot be used on the bearing cap in combination with bellows kit DADB.



Dimensions and ordering data

| For Ø | TD | TK | TM | UM | UW | XH | XL | | CRC ¹⁾ | Weight | Part no. | Type |
|-------|----------------------|----|----|-----|----|------|-------|---------|-------------------|--------|----------|-----------|
| [mm] | ∅ -0.01/ -0.05 | | | | | | | DSNU-KP | | [g] | | |
| 8, 10 | 4 | 6 | 26 | 38 | 20 | 13 | 65 | 94 | 1 | 20 | 8608 | WBN-8/10 |
| 12 | 6 | 8 | 38 | 58 | 25 | 18 | 76 | 114 | 1 | 51 | 8609 | WBN-12/16 |
| 16 | 6 | 8 | 38 | 58 | 25 | 18 | 82 | 120 | 1 | 51 | 8609 | WBN-12/16 |
| 20 | 6 | 8 | 46 | 66 | 30 | 20 | 96 | 143 | 1 | 67 | 8610 | WBN-20/25 |
| 25 | 6 | 8 | 46 | 66 | 30 | 24 | 101.5 | 149.5 | 1 | 67 | 8610 | WBN-20/25 |
| 32 | 8 | 12 | 50 | 76 | 40 | 28 | 109.5 | 163 | 1 | 131 | 195863 | WBN-32 |
| 40 | 10 | 15 | 60 | 92 | 50 | 31.5 | 126.1 | 193.6 | 1 | 238 | 195864 | WBN-40 |
| 50 | 12 | 20 | 80 | 116 | 65 | 34 | 140.2 | 216.7 | 1 | 596 | 195865 | WBN-50/63 |
| 63 | 12 | 20 | 80 | 116 | 65 | 35 | 149.2 | 233.7 | 1 | 596 | 195865 | WBN-50/63 |

1) More information www.festo.com/x/topic/crc

Accessories


Clevis foot LBN/CRLBN

Material:

LBN: galvanised steel

CRLBN: High-alloy stainless steel

RoHS-compliant



Dimensions and ordering data



| For \varnothing [mm] | CM | EK \varnothing | FL | GL | HB | LE | MR | RG | UX |
|---------------------------|------|---------------------|--------------|------|-----|------|----|------|----|
| 8, 10 | 8.1 | 4 | 24 +0.3/-0.2 | 13.8 | 4.5 | 21.5 | 5 | 12.5 | 20 |
| 12, 16 | 12.1 | 6 | 27 +0.3/-0.2 | 13 | 5.5 | 24 | 7 | 15 | 25 |
| 20, 25 | 16.1 | 8 | 30 +0.4/-0.2 | 16 | 6.6 | 26 | 10 | 20 | 32 |
| 32 | 16.1 | 10 | 35 +0.4/-0.2 | 18.5 | 6.6 | 31 | 11 | 24 | 35 |
| 40 | 18.1 | 12 | 40 +0.4/-0.2 | 24.5 | 9 | 35 | 13 | 30 | 45 |
| 50, 63 | 21.1 | 16 | 45 +0.5/-0.2 | 28 | 9 | 39 | 14 | 34 | 50 |

| For \varnothing [mm] | Basic version | | | | High corrosion protection | | | |
|---------------------------|-------------------|------------|---------------|------------------|---------------------------|------------|---------------|--------------------|
| | CRC ¹⁾ | Weight [g] | Part no. | Type | CRC ¹⁾ | Weight [g] | Part no. | Type |
| 8, 10 | 1 | 20 | 6057 | LBN-8/10 | - | - | - | |
| 12, 16 | 1 | 40 | 6058 | LBN-12/16 | 4 | 39 | 161862 | CRLBN-12/16 |
| 20, 25 | 1 | 84 | 6059 | LBN-20/25 | 4 | 82 | 161863 | CRLBN-20/25 |
| 32 | 1 | 110 | 195860 | LBN-32 | 4 | 106 | 195866 | CRLBN-32 |
| 40 | 1 | 191 | 195861 | LBN-40 | 4 | 185 | 195867 | CRLBN-40 |
| 50, 63 | 1 | 300 | 195862 | LBN-50/63 | 4 | 283 | 195868 | CRLBN-50/63 |



1) More information www.festo.com/x/topic/crc

Accessories

Ordering data – Piston rod attachments

| Designation | For Ø | Part no. | Type |
|--|-------|-------------|--------------|
| Rod eye SGS | | | |
|  | 8 | 9253 | SGS-M4 |
| | 10 | | |
| | 12 | 9254 | SGS-M6 |
| | 16 | | |
| | 20 | | |
| | 25 | 9255 | SGS-M8 |
| | 32 | 9261 | SGS-M10x1.25 |
| | 40 | | |
| | 50 | 9262 | SGS-M12x1.25 |
| | 63 | 9263 | SGS-M16x1.5 |
| Self-aligning rod coupler FK | | | |
|  | 8 | 6528 | FK-M4 |
| | 10 | | |
| | 12 | 2061 | FK-M6 |
| | 16 | | |
| | 20 | | |
| | 25 | 2062 | FK-M8 |
| | 32 | 6140 | FK-M10x1.25 |
| | 40 | | |
| | 50 | 6141 | FK-M12x1.25 |
| | 63 | 6142 | FK-M16x1.5 |
| Rod clevis SG | | | |
|  | 8 | 6532 | SG-M4 |
| | 10 | | |
| | 12 | 3110 | SG-M6 |
| | 16 | | |
| | 20 | | |
| | 25 | 3111 | SG-M8 |
| | 32 | 6144 | SG-M10x1.25 |
| | 40 | | |
| | 50 | 6145 | SG-M12x1.25 |
| | 63 | 6146 | SG-M16x1.5 |
| Coupling piece KSZ | | | |
|  | 12 | 36123 | KSZ-M6 |
| | 16 | | |
| | 20 | 36124 | KSZ-M8 |
| | 25 | | |
| | 32 | | |
| | 40 | 36125 | KSZ-M10x1.25 |
| | 50 | 36126 | KSZ-M12x1.25 |
| | 63 | | |
| 63 | 36127 | KSZ-M16x1.5 | |

Datasheets → Internet: piston rod attachment


| Designation | For Ø | Part no. | Type | | |
|---|-------|----------|-------------|-------|--------------|
| Rod clevis SGA | | | | | |
|  | 8 | - | | | |
| | 10 | | | | |
| | 12 | | | | |
| | 16 | | | | |
| | 20 | | | | |
| | 25 | | | | |
| | 32 | | | 32954 | SGA-M10x1.25 |
| | 40 | | | 10767 | SGA-M12x1.25 |
| | 50 | | | 10768 | SGA-M16x1.5 |
| | 63 | | | | |
| Self-aligning rod coupler DARP | | | | | |
|  | 8 | 8170110 | DARP-M4-F | | |
| | 10 | | | | |
| | 12 | 8170115 | DARP-M6-F | | |
| | 16 | | | | |
| | 20 | | | | |
| | 25 | 8170116 | DARP-M8-F | | |
| | 32 | 8170119 | DARP-M10P-F | | |
| | 40 | | | | |
| | 50 | 8170120 | DARP-M12P-F | | |
| | 63 | 8170121 | DARP-M16P-F | | |
| Coupling piece KSG | | | | | |
|  | 8 | - | | | |
| | 10 | | | | |
| | 12 | | | | |
| | 16 | | | | |
| | 20 | | | | |
| | 25 | | | 32963 | KSG-M10x1.25 |
| | 32 | | | 32964 | KSG-M12x1.25 |
| | 40 | | | | |
| | 50 | | | 32965 | KSG-M16x1.5 |
| | 63 | | | | |
| Hex nut MSK | | | | | |
|  | 16 | 189007 | MSK-M16x1.5 | | |
| | 20 | | | | |
| | 25 | 189009 | MSK-M22x1.5 | | |

Accessories

Ordering data – Piston-rod attachments, corrosion-resistant

| Designation | For Ø | Part no. | Type |
|---|-------|----------|----------------|
| Rod eye CRSGS | | | |
|  | 12 | 195580 | CRSGS-M6 |
| | 16 | | |
| | 20 | 195581 | CRSGS-M8 |
| | 25 | | |
| | 32 | 195582 | CRSGS-M10x1.25 |
| | 40 | | |
| | 50 | 195583 | CRSGS-M12x1.25 |
| | 63 | 195584 | CRSGS-M16x1.5 |
| Self-aligning rod coupler CRFK | | | |
|  | 25 | 2305778 | CRFK-M10x1.25 |
| | 32 | | |
| | 40 | 2305779 | CRFK-M12x1.25 |
| | 50 | 2490673 | CRFK-M16x1.5 |
| | 63 | | |

Datasheets → Internet: piston rod attachment

| Designation | For Ø | Part no. | Type |
|---|-------|----------|---------------|
| Rod clevis CRSG | | | |
|  | 8 | 8165295 | CRSG-M4 |
| | 12 | 13567 | CRSG-M6 |
| | 16 | | |
| | 20 | 13568 | CRSG-M8 |
| | 25 | 13569 | CRSG-M10x1.25 |
| | 32 | | |
| | 40 | 13570 | CRSG-M12x1.25 |
| | 50 | 13571 | CRSG-M16x1.5 |
| 63 | | | |


Ordering data – Mounting components

| Designation | For Ø | Part no. | Type |
|--|-------|----------|--------|
| Clevis foot LBG | | | |
|  | 32 | 31761 | LBG-32 |
| | 40 | 31762 | LBG-40 |
| | 50 | 31763 | LBG-50 |
| | 63 | 31764 | LBG-63 |

Datasheets → Internet: clevis foot

| Designation | For Ø | Part no. | Type |
|--|-------|----------|--------|
| Right angle clevis foot LQG | | | |
|  | 32 | 31768 | LQG-32 |
| | 40 | 31769 | LQG-40 |
| | 50 | 31770 | LQG-50 |
| | 63 | 31771 | LQG-63 |

Ordering data – Guide units

| | For Ø | Stroke [mm] | With recirculating ball bearing guide | | With plain-bearing guide | |
|---|--------|----------------|---------------------------------------|------------------|--------------------------|------------------|
| | | | Part no. | Type | Part no. | Type |
|  | 8, 10 | 1 ... 100 | 35197 | FEN-8/10-...-KF | 35196 | FEN-8/10-...-GF |
| | 12, 16 | 1 ... 200 | 33481 | FEN-12/16-...-KF | 19168 | FEN-12/16-...-GF |
| | 20 | 2 ... 250 | 33482 | FEN-20-...-KF | 19169 | FEN-20-...-GF |
| | 25 | 2 ... 250 | 33483 | FEN-25-...-KF | 19170 | FEN-25-...-GF |

Datasheets → Internet: feng

Accessories

Bellows kit DADB




| General technical data | | | | | | | | |
|---|------|---|------------|------------|------------|----|----|----|
| Type DADB-S1- | 12 | 16 | 20 | 25 | 32 | 40 | 50 | 63 |
| Max. stroke range of the cylinder ¹⁾ | | | | | | | | |
| DSNU | [mm] | 10 ... 200 | 10 ... 200 | 10 ... 320 | 10 ... 500 | | | |
| Type of mounting | | Via threaded pin | | | | | | |
| Mounting position | | Any | | | | | | |
| Media resistance | | Dust, chippings, oil, grease, fuel (→ Internet: media resistance) | | | | | | |
| Ambient temperature ²⁾ | [°C] | -10 ... +80 | | | | | | |
| Corrosion resistance class CRC ³⁾ | | 3 - High corrosion stress | | | | | | |

- 1) In conjunction with the bellows kit DADB
- 2) Note operating range of proximity switches and cylinder
- 3) More information www.festo.com/x/topic/crc

Materials

Sectional view



| Bellows | |
|---|--|
| [1] Connection | Polyamide |
| [2] Intermediate piece | Polyamide |
| [3] Bellows | NBR |
| [4] End piece | Polyamide |
| - O-ring | NBR |
| Note on materials | RoHS-compliant |
| Suitable for the production of Li-ion batteries | Suitable for battery production with reduced Cu/Zn/Ni values (F1a) |

Accessories

| Weight [g] | | | | |
|------------------------------|----|----|-----|-----|
| Type DADB-S1- Stroke [mm] | 12 | 16 | 20 | 25 |
| 10 ... 50 | 7 | 7 | 20 | 19 |
| 51 ... 100 | 9 | 9 | 32 | 31 |
| 101 ... 150 | 13 | 13 | 45 | 44 |
| 151 ... 200 | 16 | 16 | 58 | 57 |
| 201 ... 250 | – | – | 73 | 72 |
| 251 ... 300 | – | – | 85 | 84 |
| 301 ... 350 | – | – | 100 | 98 |
| 351 ... 400 | – | – | – | 109 |
| 401 ... 450 | – | – | – | 124 |
| 451 ... 500 | – | – | – | 136 |

| Type DADB-S1- Stroke [mm] | 32 | 40 | 50 | 63 |
|------------------------------|-----|-----|-----|-----|
| 10 ... 50 | 29 | 34 | 55 | 55 |
| 51 ... 125 | 41 | 49 | 75 | 75 |
| 126 ... 175 | 51 | 60 | 89 | 89 |
| 176 ... 250 | 66 | 78 | 113 | 113 |
| 251 ... 300 | 79 | 93 | 131 | 131 |
| 301 ... 350 | 92 | 108 | 149 | 149 |
| 351 ... 375 | 92 | 108 | 151 | 151 |
| 376 ... 425 | 104 | 122 | 169 | 169 |
| 426 ... 475 | 117 | 137 | 187 | 187 |
| 476 ... 500 | 117 | 137 | 189 | 189 |



Accessories

Travel speed v as a function of tubing length l



The bellows kit is a leak-free system. To prevent unwanted media from being drawn in, the supply or exhaust air of the kit is ducted in the connection part via a pressure compensation opening. The pressure generated in the bellows kit by the positioning motion is primarily defined by the travel speed and tubing length. The recommended tube length in relation to the travel speed of the drive can be read from the diagram.



Advancing



— DSNU-12/16
- - - DSNU-20/25

— DSNU-32/50/63
- - - DSNU-40

Retracting



— DSNU-12/16
- - - DSNU-20/25

— DSNU-32
- - - DSNU-40
- - - DSNU-50/63


Note
The push-in fittings in the adjacent table must be used for the pressure compensation hole. Silencers can be used as an alternative. This reduces the travel speed slightly.

| Tubing size and push-in fitting for pressure compensation hole | | | |
|--|------------------|-----------------|--------------------|
| ∅ [mm] | Tubing O.D. [mm] | Push-in fitting | |
| | | Part no. | Type |
| 12, 16, 20, 25 | 6 | 153317 | QSM-M5-6-I |
| | | 578371 | NPQH-DK-M5-Q6-P10 |
| | | 578335 | NPQH-D-M5-Q6-P10 |
| | | 578359 | NPQH-D-M5-S6-P10 |
| 32, 40 | 8 | 186109 | QS-G1/8-8-I |
| | | 578376 | NPQH-DK-G18-Q8-P10 |
| | | 578362 | NPQH-D-G18-S8-P10 |
| 50, 63 | 12 | 186350 | QS-G1/4-12 |
| | | 578344 | NPQH-D-G14-Q12-P10 |
| | | 578366 | NPQH-D-G14-S12-P10 |

Accessories

Dimensions

Download CAD data → www.festo.com



| ∅ Stroke [mm] | 12/16 | | | | | | | 20 | | | | | | |
|------------------|------------------|-----------------|---------|----|----|-----|-------|------------------|-----------------|---------|----|-----|-----|-------|
| | A2 ¹⁾ | D1 ∅ max. | D2 ∅ | EE | L1 | L2 | WF+A2 | A2 ¹⁾ | D1 ∅ max. | D2 ∅ | EE | L1 | L2 | WF+A2 |
| 10 ... 50 | 23 | 22 | 8.5 | M5 | 5 | 3.2 | 45 | 22 | 29 | 8.5 | M5 | 4.2 | 2.7 | 46 |
| 51 ... 100 | 34 | | | | | | 56 | 34 | | | | | | 58 |
| 101 ... 150 | 48 | | | | | | 70 | 47 | | | | | | 71 |
| 151 ... 200 | 59 | | | | | | 81 | 60 | | | | | | 84 |
| 201 ... 250 | – | | | | | | – | 75 | | | | | | 99 |
| 251 ... 300 | – | | | | | | – | 86 | | | | | | 110 |
| 301 ... 350 | – | | | | | | – | 101 | | | | | | 125 |
| 351 ... 400 | – | | | | | | – | – | | | | | | – |
| 401 ... 450 | – | | | | | | – | – | | | | | | – |
| 451 ... 500 | – | | | | | | – | – | | | | | | – |


| ∅ Stroke [mm] | 25 | | | | | | |
|------------------|------------------|-----------------|---------|----|-----|-----|-------|
| | A2 ¹⁾ | D1 ∅ max. | D2 ∅ | EE | L1 | L2 | WF+A2 |
| 10 ... 50 | 22 | 29 | 8.5 | M5 | 4.2 | 2.7 | 50 |
| 51 ... 100 | 34 | | | | | | 62 |
| 101 ... 150 | 47 | | | | | | 75 |
| 151 ... 200 | 60 | | | | | | 88 |
| 201 ... 250 | 75 | | | | | | 103 |
| 251 ... 300 | 86 | | | | | | 114 |
| 301 ... 350 | 101 | | | | | | 129 |
| 351 ... 400 | 112 | | | | | | 140 |
| 401 ... 450 | 127 | | | | | | 155 |
| 451 ... 500 | 138 | | | | | | 166 |

1) The dimension corresponds to the K8 value (extended piston rod) of the drive

Accessories

Dimensions

Download CAD data → www.festo.com



| ∅ Stroke [mm] | 32 | | | | | | | 40 | | | | | | |
|------------------|------------------|-----------------|---------|------|------|-----|-------|------------------|-----------------|---------|------|-----|-----|-------|
| | A2 ¹⁾ | D1 ∅ max. | D2 ∅ | EE | L1 | L2 | WF+A2 | A2 ¹⁾ | D1 ∅ max. | D2 ∅ | EE | L1 | L2 | WF+A2 |
| 10 ... 50 | 30 | 38 | 14 | G1/8 | 12.9 | 5.4 | 64 | 29 | 46 | 14 | G1/8 | 8.1 | 5.4 | 68 |
| 51 ... 125 | 48 | | | | | | 82 | 44 | | | | | | 83 |
| 126 ... 175 | 63 | | | | | | 97 | 57 | | | | | | 96 |
| 176 ... 250 | 82 | | | | | | 116 | 73 | | | | | | 112 |
| 251 ... 300 | 97 | | | | | | 131 | 87 | | | | | | 126 |
| 301 ... 350 | 113 | | | | | | 147 | 101 | | | | | | 140 |
| 351 ... 375 | 115 | | | | | | 149 | 102 | | | | | | 141 |
| 376 ... 425 | 131 | | | | | | 165 | 116 | | | | | | 155 |
| 426 ... 475 | 147 | | | | | | 181 | 131 | | | | | | 170 |
| 476 ... 500 | 149 | | | | | | 183 | 132 | | | | | | 171 |

| ∅ Stroke [mm] | 50/63 | | | | | | |
|------------------|------------------|-----------------|---------|------|-------|----|---------|
| | A2 ¹⁾ | D1 ∅ max. | D2 ∅ | EE | L1 | L2 | WF+A2 |
| 10 ... 50 | 30 | 57 | 17 | G1/4 | 10.65 | 7 | 74/75 |
| 51 ... 125 | 48 | | | | | | 92/93 |
| 126 ... 175 | 58 | | | | | | 102/103 |
| 176 ... 250 | 77 | | | | | | 121/122 |
| 251 ... 300 | 88 | | | | | | 132/133 |
| 301 ... 350 | 99 | | | | | | 143/144 |
| 351 ... 375 | 106 | | | | | | 150/151 |
| 376 ... 425 | 117 | | | | | | 161/162 |
| 426 ... 475 | 128 | | | | | | 172/173 |
| 476 ... 500 | 135 | | | | | | 179/180 |

1) The dimension corresponds to the K8 value (extended piston rod) of the drive

Accessories

Ordering data – Bellows kit

An extended piston rod (order code K8) is absolutely essential when using a bellows kit → Ordering data – Modular product system.

The necessary dimension for K8 as a function of piston diameter and cylinder stroke as well as the corresponding bellows kit is indicated in the table below:

Order example:

Selected round cylinder:

DSNU-25-320-PPV-A-MQ-...

The dimension for the corresponding K8 value (see table): 101 mm

Complete order reference for round cylinder:


DSNU-25-320-PPV-A-MQ-...-101K8


The corresponding bellows kit:


DADB-S1-25-S301-350

| Cylinder data | | | Bellows kit | | |
|---------------|-------------|------------------|---------------------|---------------------|---------------------|
| ∅ | Stroke | Dimension for K8 | Part no. | Type | |
| [mm] | [mm] | [mm] | | | |
| 12 | 10 ... 50 | 23 | 553391 | DADB-S1-12-S10-50 | |
| | 51 ... 100 | 34 | 553393 | DADB-S1-12-S51-100 | |
| | 101 ... 150 | 48 | 553395 | DADB-S1-12-S101-150 | |
| | 151 ... 200 | 59 | 553397 | DADB-S1-12-S151-200 | |
| 20 | 10 ... 50 | 22 | 553407 | DADB-S1-20-S10-50 | |
| | 51 ... 100 | 34 | 553409 | DADB-S1-20-S51-100 | |
| | 101 ... 150 | 47 | 553411 | DADB-S1-20-S101-150 | |
| | 151 ... 200 | 60 | 553413 | DADB-S1-20-S151-200 | |
| | 201 ... 250 | 75 | 553415 | DADB-S1-20-S201-250 | |
| | 251 ... 300 | 86 | 553417 | DADB-S1-20-S251-300 | |
| | 301 ... 320 | 101 | 553419 | DADB-S1-20-S301-350 | |
| 32 | 10 ... 50 | 30 | 553441 | DADB-S1-32-S10-50 | |
| | 51 ... 125 | 48 | 553443 | DADB-S1-32-S51-125 | |
| | 126 ... 175 | 63 | 553445 | DADB-S1-32-S126-175 | |
| | 176 ... 250 | 82 | 553447 | DADB-S1-32-S176-250 | |
| | 251 ... 300 | 97 | 553449 | DADB-S1-32-S251-300 | |
| | 301 ... 350 | 113 | 553451 | DADB-S1-32-S301-350 | |
| | 351 ... 375 | 115 | 553453 | DADB-S1-32-S351-375 | |
| | 376 ... 425 | 131 | 553455 | DADB-S1-32-S376-425 | |
| | 426 ... 475 | 147 | 553457 | DADB-S1-32-S426-475 | |
| 476 ... 500 | 149 | 553459 | DADB-S1-32-S476-500 | | |
| 50 | 10 ... 50 | 30 | 553481 | DADB-S1-50-S10-50 | |
| | 51 ... 125 | 48 | 553483 | DADB-S1-50-S51-125 | |
| | 126 ... 175 | 58 | 553485 | DADB-S1-50-S126-175 | |
| | 176 ... 250 | 77 | 553487 | DADB-S1-50-S176-250 | |
| | 251 ... 300 | 88 | 553489 | DADB-S1-50-S251-300 | |
| | 301 ... 350 | 99 | 553491 | DADB-S1-50-S301-350 | |
| | 351 ... 375 | 106 | 553493 | DADB-S1-50-S351-375 | |
| | 376 ... 425 | 117 | 553495 | DADB-S1-50-S376-425 | |
| | 426 ... 475 | 128 | 553497 | DADB-S1-50-S426-475 | |
| | 476 ... 500 | 135 | 553499 | DADB-S1-50-S476-500 | |
| | 63 | 10 ... 50 | 30 | 553501 | DADB-S1-63-S10-50 |
| 51 ... 125 | | 48 | 553503 | DADB-S1-63-S51-125 | |
| 126 ... 175 | | 58 | 553505 | DADB-S1-63-S126-175 | |
| 176 ... 250 | | 77 | 553507 | DADB-S1-63-S176-250 | |
| 251 ... 300 | | 88 | 553509 | DADB-S1-63-S251-300 | |
| 301 ... 350 | | 99 | 553511 | DADB-S1-63-S301-350 | |
| 351 ... 375 | | 106 | 553513 | DADB-S1-63-S351-375 | |
| 376 ... 425 | | 117 | 553515 | DADB-S1-63-S376-425 | |
| 426 ... 475 | | 128 | 553517 | DADB-S1-63-S426-475 | |
| 476 ... 500 | | 135 | 553519 | DADB-S1-63-S476-500 | |
| 16 | | 10 ... 50 | 23 | 553399 | DADB-S1-16-S10-50 |
| | 51 ... 100 | 34 | 553401 | DADB-S1-16-S51-100 | |
| | 101 ... 150 | 48 | 553403 | DADB-S1-16-S101-150 | |
| | 151 ... 200 | 59 | 553405 | DADB-S1-16-S151-200 | |
| | 25 | 10 ... 50 | 22 | 553421 | DADB-S1-25-S10-50 |
| | | 51 ... 100 | 34 | 553423 | DADB-S1-25-S51-100 |
| | | 101 ... 150 | 47 | 553425 | DADB-S1-25-S101-150 |
| | | 151 ... 200 | 60 | 553427 | DADB-S1-25-S151-200 |
| | | 201 ... 250 | 75 | 553429 | DADB-S1-25-S201-250 |
| | | 251 ... 300 | 86 | 553431 | DADB-S1-25-S251-300 |
| | | 301 ... 350 | 101 | 553433 | DADB-S1-25-S301-350 |
| 351 ... 400 | | 112 | 553435 | DADB-S1-25-S351-400 | |
| 401 ... 450 | | 127 | 553437 | DADB-S1-25-S401-450 | |
| 451 ... 500 | 138 | 553439 | DADB-S1-25-S451-500 | | |
| 40 | 10 ... 50 | 29 | 553461 | DADB-S1-40-S10-50 | |
| | 51 ... 125 | 44 | 553463 | DADB-S1-40-S51-125 | |
| | 126 ... 175 | 57 | 553465 | DADB-S1-40-S126-175 | |
| | 176 ... 250 | 73 | 553467 | DADB-S1-40-S176-250 | |
| | 251 ... 300 | 87 | 553469 | DADB-S1-40-S251-300 | |
| | 301 ... 350 | 101 | 553471 | DADB-S1-40-S301-350 | |
| | 351 ... 375 | 102 | 553473 | DADB-S1-40-S351-375 | |
| | 376 ... 425 | 116 | 553475 | DADB-S1-40-S376-425 | |
| | 426 ... 475 | 131 | 553477 | DADB-S1-40-S426-475 | |
| 476 ... 500 | 132 | 553479 | DADB-S1-40-S476-500 | | |

Accessories

| Ordering data – Proximity switch for T-slot, magneto-resistive | | | | | | Datasheets → Internet: smt |
|--|--|-----------------------|------------------|----------|---------|----------------------------|
| Type of mounting | Switching output | Electrical connection | Cable length [m] | Part no. | Type | |
| N/O | | | | | | |
|  | Inserted in the slot from above, flush with the cylinder profile, short design | PNP | Cable, 3-core | 2.5 | 574335 | SMT-8M-A-PS-24V-E-2.5-OE |
| | | | Cable, 2-core | 5 | 8165237 | SMT-8M-A-ZS-24V-E-5.0-OE |
| | | | Plug M8x1, 3-pin | 0.3 | 574334 | SMT-8M-A-PS-24V-E-0.3-M8D |
| | | NPN | Cable, 3-core | 2.5 | 574338 | SMT-8M-A-NS-24V-E-2.5-OE |
| | | | Plug M8x1, 3-pin | 0.3 | 574339 | SMT-8M-A-NS-24V-E-0.3-M8D |



| Ordering data – Proximity switch for T-slot, magneto-resistive | | | | | | Datasheets → Internet: crsmt |
|--|--|-----------------------|-------------------|----------|--------|------------------------------|
| Type of mounting | Switching output | Electrical connection | Cable length [m] | Part no. | Type | |
| N/O | | | | | | |
|  | Inserted in the slot from above, flush with the cylinder profile | PNP | Cable, 3-core | 5.0 | 574380 | CRSMT-8M-PS-24V-K-5.0-OE |
| | | | Cable, 3-core | 10.0 | 574381 | CRSMT-8M-PS-24V-K-10.0-OE |
| | | | Plug M8x1, 3-pin | 0.3 | 574383 | CRSMT-8M-PS-24V-K-0.3-M8D |
| | | | Plug M12x1, 3-pin | 0.3 | 574382 | CRSMT-8M-PS-24V-K-0.3-M12 |

| Ordering data – Proximity switch for T-slot, magnetic Hall | | | | | | Datasheets → Internet: sdbt |
|---|--|------------------------|------------------|----------|---------|-----------------------------|
| Type of mounting | Switching output | Electrical connection | Cable length [m] | Part no. | Type | |
| N/O or N/C contact, switchable | | | | | | |
|  | Inserted in the slot from above, flush with the cylinder profile, short design | PNP, switchable to NPN | Plug M8x1, 3-pin | 0.3 | 8059120 | SDBT-MSX-1L-PU-E-0.3-N-M8 |
| | | | Cable, 3-core | 2.5 | 8059121 | SDBT-MSX-1L-PU-E-2.5-N-LE |
| | | NPN, switchable to PNP | Plug M8x1, 3-pin | 0.3 | 8059123 | SDBT-MSX-1L-NU-E-0.3-N-M8 |
| | | | Cable, 3-core | 2.5 | 8059124 | SDBT-MSX-1L-NU-E-2.5-N-LE |

| Ordering data – Mounting kits for proximity switches | | | | Datasheets → Internet: smbr |
|--|--------|-----------|-----------|-----------------------------|
| Designation | For Ø | Part no. | Type | |
| Mounting kit SMBR-8 | | | | |
|  | 8 | 175091 | SMBR-8-8 | |
| | 10 | 175092 | SMBR-8-10 | |
| | 12 | 175093 | SMBR-8-12 | |
| | 16 | 175094 | SMBR-8-16 | |
| | 20 | 175095 | SMBR-8-20 | |
| | 25 | 175096 | SMBR-8-25 | |
| | 32 | 175097 | SMBR-8-32 | |
| | 40 | 175098 | SMBR-8-40 | |
| | 50 | 175099 | SMBR-8-50 | |
| 63 | 175100 | SMBR-8-63 | | |

| Ordering data – Mounting kits for proximity switches, temperature range S6 | | | | Datasheets → Internet: smbr |
|--|----------|----------|-----------------|-----------------------------|
| Designation | For Ø | Part no. | Type | |
| Mounting kit SMBR-8 | | | | |
|  | 8 ... 63 | 538937 | SMBR-8-8/100-S6 | |

Accessories

| Connecting cables NEBA, straight, M8 connection | | | | | | |
|---|--|--|---|--------------|----------|------------------------|
| | Electrical connection 1, connection technology | Electrical connection 2, connection technology | Electrical connection 2, number of pins/cores | Cable length | Part no. | Type |
|  | M8x1 A-coded to EN 61076-2-104 | Open end | 3 | 2.5 m | 8078223 | NEBA-M8G3-U-2.5-N-LE3 |
| | | | | 5 m | 8078224 | NEBA-M8G3-U-5-N-LE3 |
| Connecting cables NEBA, straight, M12 connection | | | | | | |
| | Electrical connection 1, connection technology | Electrical connection 2, connection technology | Electrical connection 2, number of pins/cores | Cable length | Part no. | Type |
|  | M12x1, A-coded to EN 61076-2-101 | Open end | 3 | 2.5 m | 8078236 | NEBA-M12G5-U-2.5-N-LE3 |
| | | | | 5 m | 8078237 | NEBA-M12G5-U-5-N-LE3 |
| Connecting cables NEBA, angled, M8 connection | | | | | | |
| | Electrical connection 1, connection technology | Electrical connection 2, connection technology | Electrical connection 2, number of pins/cores | Cable length | Part no. | Type |
|  | M8x1 A-coded to EN 61076-2-104 | Open end | 3 | 2.5 m | 8078230 | NEBA-M8W3-U-2.5-N-LE3 |
| | | | | 5 m | 8078231 | NEBA-M8W3-U-5-N-LE3 |
| Connecting cables NEBA, angled, M12 connection | | | | | | |
| | Electrical connection 1, connection technology | Electrical connection 2, connection technology | Electrical connection 2, number of pins/cores | Cable length | Part no. | Type |
|  | M12x1, A-coded to EN 61076-2-101 | Open end | 3 | 2.5 m | 8078245 | NEBA-M12W5-U-2.5-N-LE3 |
| | | | | 5 m | 8078246 | NEBA-M12W5-U-5-N-LE3 |

Accessories

Position transmitter

The position transmitter continuously senses the position of the piston.

It has an analogue output with an output signal that is proportional to the piston position.


Ordering data – Position transmitter for T-slot

Datasheets → Internet: sdas

| | Position measuring range | Description | Type of mounting | Electrical connection | Cable length [m] | Part no. | Type |
|--|--------------------------|--|---------------------------------|------------------------------|------------------|----------------|---|
|  | ≤ 52 | Choice of two operating modes: • Two adjustable switching outputs • IO-Link® | Inserted in the slot from above | Plug M8x1, 4-pin, lengthwise | 0.3 | 8063974 | SDAS-MHS-M40-1L-PNLK-PN-E-0.3-M8 |


Ordering data – Position transmitter for T-slot

Datasheets → Internet: sdat

| | Position measuring range | Analogue output | | Type of mounting | Electrical connection | Cable length [m] | Part no. | Type |
|--|--------------------------|-----------------|----------|---------------------------------|------------------------------|------------------|----------------|-------------------------------------|
| | | [V] | [mA] | | | | | |
|  | 0 ... 50 | – | 4 ... 20 | Inserted in the slot from above | Plug M8x1, 4-pin, lengthwise | 0.3 | 1531265 | SDAT-MHS-M50-1L-SA-E-0.3-M8 |
| | 0 ... 80 | | | | | | 1531266 | SDAT-MHS-M80-1L-SA-E-0.3-M8 |
| | 0 ... 100 | | | | | | 1531267 | SDAT-MHS-M100-1L-SA-E-0.3-M8 |
| | 0 ... 125 | | | | | | 1531268 | SDAT-MHS-M125-1L-SA-E-0.3-M8 |
| | 0 ... 160 | | | | | | 1531269 | SDAT-MHS-M160-1L-SA-E-0.3-M8 |

Ordering data – Position transmitter for T-slot

Datasheets → Internet: smat


| | Position measuring range | Analogue output | | Type of mounting | Electrical connection | Cable length [m] | Part no. | Type |
|--|--------------------------|-----------------|------|---------------------------------|------------------------------|------------------|---------------|----------------------------|
| | | [V] | [mA] | | | | | |
|  | 0 ... 40 | 0 ... 10 | – | Inserted in the slot from above | Plug M8x1, 4-pin, lengthwise | 0.3 | 553744 | SMAT-8M-U-E-0.3-M8D |


Ordering data – Mounting kits for position transmitters


Datasheets → Internet: smbr

| Designation | For Ø | Part no. | Type |
|--|-------|---------------|------------------|
| Mounting kit SMBR-8 | | | |
|  | 8 | 175091 | SMBR-8-8 |
| | 10 | 175092 | SMBR-8-10 |
| | 12 | 175093 | SMBR-8-12 |
| | 16 | 175094 | SMBR-8-16 |
| | 20 | 175095 | SMBR-8-20 |
| | 25 | 175096 | SMBR-8-25 |
| | 32 | 175097 | SMBR-8-32 |
| | 40 | 175098 | SMBR-8-40 |
| | 50 | 175099 | SMBR-8-50 |
| | 63 | 175100 | SMBR-8-63 |

Accessories

| Ordering data – Mounting kits for position transmitters, temperature range S6 | | | | Datasheets → Internet: smbr | |
|---|----------|----------|-----------------|-----------------------------|--|
| Designation | For Ø | Part no. | Type | | |
| Mounting kit SMBR-8 | | | | | |
|  | 8 ... 63 | 538937 | SMBR-8-8/100-S6 | | |

| Connecting cables NEBA, straight | | | | | | |
|---|--|--|---|--------------|----------|-----------------------|
| | Electrical connection 1, connection technology | Electrical connection 2, connection technology | Electrical connection 2, number of pins/cores | Cable length | Part no. | Type |
|  | M8x1 A-coded to EN 61076-2-104 | Open end | 4 | 2.5 m | 8078227 | NEBA-M8G4-U-2.5-N-LE4 |
| | | | | 5 m | 8078228 | NEBA-M8G4-U-5-N-LE4 |

| Connecting cables NEBA, angled | | | | | | |
|--|--|--|---|--------------|----------|-----------------------|
| | Electrical connection 1, connection technology | Electrical connection 2, connection technology | Electrical connection 2, number of pins/cores | Cable length | Part no. | Type |
|  | M8x1 A-coded to EN 61076-2-104 | Open end | 4 | 2.5 m | 8078233 | NEBA-M8W4-U-2.5-N-LE4 |
| | | | | 5 m | 8078234 | NEBA-M8W4-U-5-N-LE4 |

| Ordering data – One-way flow control valves | | | | | Datasheets → Internet: grl | | |
|---|-------------------|-----------------|--------------|------------------|----------------------------|-----------------|--|
| | Connection Thread | For tubing O.D. | Material | Part no. | Type | | |
| For exhaust air | | | | | | | |
|  | M5 | 3 | Metal design | 193137 | GRLA-M5-QS-3-D | | |
| | | 4 | | 193138 | GRLA-M5-QS-4-D | | |
| | | 6 | | 193139 | GRLA-M5-QS-6-D | | |
| | G1/8 | 3 | | 193142 | GRLA-1/8-QS-3-D | | |
| | | 4 | | 193143 | GRLA-1/8-QS-4-D | | |
| | | 6 | | 193144 | GRLA-1/8-QS-6-D | | |
| | G1/4 | 8 | | 193145 | GRLA-1/8-QS-8-D | | |
| | | 6 | | 193146 | GRLA-1/4-QS-6-D | | |
| | | 8 | | 193147 | GRLA-1/4-QS-8-D | | |
| | G3/8 | 10 | | 193148 | GRLA-1/4-QS-10-D | | |
| | | 6 | | 193149 | GRLA-3/8-QS-6-D | | |
| | | 8 | | 193150 | GRLA-3/8-QS-8-D | | |
| | | 10 | 193151 | GRLA-3/8-QS-10-D | | | |
| For supply air | | | | | | | |
|  | M5 | 3 | Metal design | 193153 | GRLZ-M5-QS-3-D | | |
| | | 4 | | 193154 | GRLZ-M5-QS-4-D | | |
| | | 6 | | 193155 | GRLZ-M5-QS-6-D | | |
| | G1/8 | 3 | | 193156 | GRLZ-1/8-QS-3-D | | |
| | | 4 | | 193157 | GRLZ-1/8-QS-4-D | | |
| | | 6 | | 193158 | GRLZ-1/8-QS-6-D | | |
| | | | | 8 | 193159 | GRLZ-1/8-QS-8-D | |