

Toothed belt axes ELGG

FESTO



Toothed belt axes ELGG


Key features

FESTO


At a glance

- Toothed belt axis with two opposing slides
- Optimum price/performance ratio
- Ready-to-install unit for quick and easy design
- High reliability thanks to a tested service life of 2,500 km per slide
- Motor can be mounted on four sides using identical mounting accessories
- Complete kit for a simple and space-saving solution for end-position sensing
- Plain-bearing guide
 - For small loads
 - Restricted operating behaviour with torque load
 - Guide backlash = 0.05 mm (on delivery)
- Recirculating ball bearing guide
 - For medium loads
 - Very good operating behaviour with torque load
 - Backlash-free guide (preloaded guide elements)

Opposing movement, controlled via a motor



Optionally with central support to increase the forces and torques per slide




Application examples

- Suitable for sorting, separating and spreading
- For opening doors
- For gripping tasks with small loads
- Positioning and handling with low process forces
- Centring and aligning

Characteristic values of the axes

The specifications shown in the table are maximum values.

The precise values for each of the variants can be found in the relevant technical data.

Version	Size	Working stroke per slide [mm]	Speed [m/s]	Repetition accuracy [mm]	Feed force ¹⁾ [N]	Guide characteristics				
						Forces and torques				
						F _y [N]	F _z [N]	M _x [Nm]	M _y [Nm]	M _z [Nm]
	35	50 ... 700	3	±0.1	50	50	50	2.5	20	20
	45	50 ... 900	3	±0.1	100	100	100	5	40	40
	55	50 ... 1,200	3	±0.1	350	300	300	15	124	124

1) Combined feed force of both slides

Note

PositioningDrives
sizing software
www.festo.com

Toothed belt axes ELGG

Key features

Complete system comprising toothed belt axis, motor, motor controller and motor mounting kit

Toothed belt axis with recirculating ball bearing guide or plain-bearing guide



Motor

→ 18



1



2

- 1 Servo motor EMMS-AS
- 2 Stepper motor EMMS-ST

Note

A range of specially adapted complete solutions is available for the toothed belt axis ELGG and the motors.

Motor controller

Technical data → Internet: motor controller



1



2

- 1 Servo motor controller CMMP-AS, CMMS-AS
- 2 Stepper motor controller CMMS-ST

Motor mounting kit

→ 18

Axial kit




Kit comprising:

- Motor flange
- Coupling housing
- Coupling
- Screws
- Slot nuts

Peripherals overview

Peripherals overview



Toothed belt axes ELGG

Peripherals overview

Variants and accessories		
Type	Brief description	→ Page/Internet
1 Slot cover NC	<ul style="list-style-type: none"> For protecting against ingress of dirt 	20
2 Centring sleeve ZBH	<ul style="list-style-type: none"> For centring loads and attachments on the slide 4 centring sleeves included in the scope of delivery of the axis 	20
3 Profile mounting MA	For mounting the axis on the bearing cap	19
4 Slot nut NM	For mounting attachments	20
5 Switching lug SA, SB	For sensing the slide position	19
6 Sensor bracket SA, SB	Adapter for mounting the inductive proximity sensors on the axis	19
7 Proximity sensor, T-slot SA, SB	<ul style="list-style-type: none"> Inductive proximity sensor, for T-slot 1 switching lug and 1 sensor bracket are included in the scope of delivery with the order code SA, SB 	20
8 Drive shaft EA	<ul style="list-style-type: none"> Can, if required, be used as an alternative interface No drive shaft is required for the axis/motor combination → 18 	20
9 Motor EMMS	Motors specially matched to the axis, with or without brake	18
10 Axial kit EAMM	For axial motor mounting (comprising: coupling, coupling housing and motor flange)	18
– Connecting cable NEBU	For proximity sensor (order code SA and SB)	20

Toothed belt axes ELGG

Type codes

FESTO

		ELGG	-	TB	-		-	45	-	500	-	30H	-	L	-		-	M
Type																		
ELGG	Linear axis																	
Drive function																		
TB	Toothed belt																	
Guide																		
-	Recirculating ball bearing guide																	
GF	Plain-bearing guide																	
Size																		
Stroke per slide [mm]																		
Stroke reserve per slide																		
Slide																		
-	Standard slide																	
L	Long slide																	
Additional slide																		
-	No additional slide																	
ZB	1 slide on right, 1 slide on left																	
Additional function																		
-	None																	
M	Central support																	

Toothed belt axes ELGG

Type codes


→		2SA		4NM	EA	2MA
Proximity sensor						
...SA	Proximity sensor (SIES), inductive, T-slot, PNP, N/O contact, cable 7.5 m					
...SB	Proximity sensor (SIES), inductive, T-slot, PNP, N/C contact, cable 7.5 m					
Cover						
...NC	For mounting slot					
Slot nut						
...NM	For mounting slot					
Drive shaft						
...EA	Drive shaft					
Profile mounting						
...MA	Profile mounting					

Toothed belt axes ELGG

Technical data


FESTO

Function



-N- Size
35 ... 55
-T- Stroke length
50 ... 1,200 mm

[www.festo.com/en/
Spare_parts_service](http://www.festo.com/en/Spare_parts_service)



General technical data				
Size		35	45	55
Design		Electromechanical linear axis with toothed belt		
Guide		Recirculating ball bearing guide		
		Plain-bearing guide		
Mounting position		Any		
Working stroke per slide	[mm]	50 ... 700	50 ... 900	50 ... 1,200
Max. feed force $F_x^{1)}$	[N]	50	100	350
Max. no-load torque	[Nm]	0.18	0.3	0.5
Max. driving torque	[Nm]	0.46	1.24	5
Max. no-load resistance to shifting	[N]	10.8	16.1	27.9
Max. speed				
Recirculating ball bearing guide	[m/s]	3		
Plain-bearing guide	[m/s]	1		
Max. acceleration ²⁾	[m/s ²]	50		
Repetition accuracy	[mm]	±0.1		

1) Combined feed force of both slides

2) The max. acceleration is dependent on the moving load, the driving torque and the max. feed force

Operating and environmental conditions			
Ambient temperature			
Recirculating ball bearing guide	[°C]	-10 ... +50	
Plain-bearing guide	[°C]	0 ... +40	
Protection class		IP20	
Duty cycle	[%]	100	

Weight [kg]			
Size	35	45	55
Recirculating ball bearing guide			
Basic weight with 0 mm stroke ¹⁾			
Standard slide	1.9	4.2	7.2
Long slide	2.6	6.0	10.3
Additional weight per 1,000 mm stroke	4.9	10.0	15.6
Moving load	0.8	1.7	2.9
Slide			
Standard slide	0.8	1.7	2.9
Long slide	1.3	3.0	5.2
Additional slide	0.6	1.5	2.6
Central support	0.2	0.5	0.7

1) Incl. 2 slides, without central support

Toothed belt axes ELGG

Technical data

Weight [kg]			
Size	35	45	55
Plain-bearing guide			
Basic weight with 0 mm stroke ¹⁾			
Standard slide	1.9	4.3	7.2
Long slide	2.7	6.2	10.8
Additional weight per 1,000 mm stroke	4.9	10.0	15.6
Moving load	0.8	1.7	3.0
Slide			
Standard slide	0.8	1.7	3.0
Long slide	1.5	3.2	5.6
Additional slide	0.6	1.5	2.6
Central support	0.2	0.5	0.7

1) Incl. 2 slides, without central support

Toothed belt			
Size	35	45	55
Pitch [mm]	2	3	3
Expansion [%]	0.094	0.08	0.21
Width [mm]	10	15	19.3
Effective diameter [mm]	18.46	24.83	28.65
Feed constant [mm/rev.]	58	78	90

Mass moment of inertia			
Size	35	45	55
J ₀			
Standard slide [kg mm ²]	76.12	289.55	656.98
Long slide [kg mm ²]	128.6	522.01	1,212.78
J _S per metre stroke [kg mm ² /m]	0.26	1.1	1.9
J _L per kg effective load [kg mm ² /kg]	85	154	205
J _W Additional slide [kg mm ²]	55	224	533


The mass moment of inertia J_A of the entire axis is calculated as follows:

$$J_A = J_0 + K \times J_W + J_S \times \text{working stroke [m]} + J_L \times m_{\text{effective load [kg]}}$$

K = Number of additional slides

Materials

Sectional view



Axis	
1 Bearing cap, profile	Anodised wrought aluminium alloy
2 Guide rods	Steel
3 Slide, profile	Anodised wrought aluminium alloy
4 Toothed belt clamping component	Beryllium bronze
5 Toothed belt	Polychloroprene with glass cord and nylon coating
6 Pulley	High-alloy stainless steel
Note on materials	RoHS-compliant
	Contains PWIS (paint-wetting impairment substances)

Toothed belt axes ELGG

Technical data

FESTO


Characteristic load values

The indicated forces and torques refer to the centre of the guide. These values must not be exceeded

during dynamic operation. Special attention must be paid to the cushioning phase.

Without central support

The point of application of force is the point where the centre of the guide and the centre point between the two bearing caps intersect.




If the axis is subjected to more than two of the indicated forces and torques simultaneously, the following

equation must be satisfied in addition to the indicated maximum loads:

With central support

The point of application of force is the point where the centre of the guide and the centre point between the bearing cap and the central support intersect.



Without central support

Calculating the load comparison factor:

$$f_v = \frac{|F_{y1,dyn} + F_{y2,dyn}|}{F_{Ymax.}} + \frac{|F_{z1,dyn} + F_{z2,dyn}|}{F_{Zmax.}} + \frac{|M_{x1,dyn} + M_{x2,dyn}|}{M_{Xmax.}} + \frac{|M_{y1,dyn} + M_{y2,dyn}|}{M_{Ymax.}} + \frac{|M_{z1,dyn} + M_{z2,dyn}|}{M_{Zmax.}} \leq 1$$

With central support

Calculating the load comparison factor:

$$f_v = \frac{|F_{y1,dyn}|}{F_{Ymax.}} + \frac{|F_{z1,dyn}|}{F_{Zmax.}} + \frac{|M_{x1,dyn}|}{M_{Xmax.}} + \frac{|M_{y1,dyn}|}{M_{Ymax.}} + \frac{|M_{z1,dyn}|}{M_{Zmax.}} \leq 1$$

$$f_v = \frac{|F_{y2,dyn}|}{F_{Ymax.}} + \frac{|F_{z2,dyn}|}{F_{Zmax.}} + \frac{|M_{x2,dyn}|}{M_{Xmax.}} + \frac{|M_{y2,dyn}|}{M_{Ymax.}} + \frac{|M_{z2,dyn}|}{M_{Zmax.}} \leq 1$$

Permissible forces and torques for a service life of 2,500 km per slide

Guide	Plain-bearing guide			Recirculating ball bearing guide		
Size	35	45	55	35	45	55
F _{Ymax.} , F _{Zmax.} [N]	50	100	300	50	100	300
Standard slide						
M _{Xmax.} [Nm]	1	2.5	5	2.5	5	15
M _{Ymax.} [Nm]	4	8	16	8	16	48
M _{Zmax.} [Nm]	4	8	16	8	16	48
Long slide						
M _{Xmax.} [Nm]	1	2.5	5	2.5	5	15
M _{Ymax.} [Nm]	10	20	40	20	40	124
M _{Zmax.} [Nm]	10	20	40	20	40	124

Toothed belt axes ELGG

Technical data

Service life


The service life of the guide depends on the load. To provide a rough indication of the service life of the

guide, the graph below plots the load comparison factor f_v against the service life.

These values are only theoretical. Consultation with your local contact person at Festo is mandatory for load

comparison factors f_v greater than 1.5.

Load comparison factor f_v as a function of service life



Example:

A user wants to move an X kg load. Using the formula $\rightarrow 10$ gives a value of 1.5 for the load comparison factor f_v . According to the graph, the guide would have a service life of


approx. 750 km. Reducing the acceleration reduces the M_z and M_y values. A load comparison factor of 1 now gives a service life of 2,500 km.

Note


PositioningDrives
sizing software
www.festo.com

Maximum acceleration a as a function of applied load m


ELGG-35



ELGG-45



ELGG-55



Note

For the plain-bearing guide (GF) it is recommended to reduce the acceleration to minimise overshoots and increase positioning accuracy.

— Horizontal
- - - Vertical


Toothed belt axes ELGG

Technical data


FESTO

Feed force F_x as a function of input torque M


ELGG-35




ELGG-45



ELGG-55



Speed v as a function of rotational speed n



Min. nominal stroke


With standard slide or long slide L with additional slide ZB

Size	35		45		55	
Variant	-/L	ZB	-/L	ZB	-/L	ZB
Min. nominal stroke [mm]	50	126	50	146	50	166

Toothed belt axes ELGG

Technical data

Stroke reserve



L18 = Nominal stroke
L19 = Stroke reserve
1 Central support


- The stroke reserve is a safety distance available on both sides of the slide in addition to the nominal stroke
- The sum of the nominal stroke and 2x stroke reserve must not exceed the maximum working stroke per slide
- The stroke reserve length can be freely selected
- The stroke reserve is defined via the “stroke reserve” attribute in the modular product system

Example:

Type ELGG-TB-45-500-20H-...
Nominal stroke = 500 mm
2x stroke reserve = 40 mm
Working stroke per slide = 540 mm
(540 mm = 500 mm + 2x 20 mm)

Working stroke reduction

With standard slide or long slide L with additional slide ZB



L7 = Slide length
L16 = Distance between both slides
L17 = Additional slide length

- With a toothed belt axis with additional slide, the working stroke is reduced by the length of the additional slide and the distance between both slides
- If the variant long slide L is ordered, the additional slide is not extended

Example:


Type ELGG-TB-35-500-...-ZR
Working stroke = 500 mm
L16 = 10 mm
L7 = 146 mm
L17 = 76 mm

Working stroke per slide with additional slide = 414 mm
(500 mm – 10 mm – 76 mm)

Dimensions – Additional slide

Size	35	45	55
Length L17 [mm]	76	96	116
Distance between the slides L16 [mm]	≥ 0		

2nd moment of area



Size	35	45	55
Iy [mm ⁴]	3.77x10 ³	1.57x10 ⁴	3.83x10 ⁴
Iz [mm ⁴]	1.89x10 ⁵	8.08x10 ⁵	1.85x10 ⁶

Recommended deflection limits

It is recommended to adhere to a maximum deflection of 0.5 mm so as not to impair the functionality of the axes. Greater deformation can result in increased friction, greater wear and reduced service life.


Toothed belt axes ELGG

Technical data

FESTO

Dimensions

Download CAD Data → www.festo.com/us/cad



Note


With the size 35 and stroke > 350 mm,
size 45 and stroke > 450 mm,
size 55 and stroke > 700 mm,
the toothed belt axis is always supplied with
central support M.

+ Plus 2x stroke + 4x stroke reserve + L11


1 Central support

Profile


ELGG-35



ELGG-45



ELGG-55



Toothed belt axes ELGG

Technical data

Size	B1	B2	B3	B4	B5	B6	B7	D1 Ø H7	D2 Ø	D3 Ø H7	D4 Ø H7	H1	H2	H3
ELGG-35	37	35	20	7.5	9.5	1	17.5	8	15	27	7	80	39	78
ELGG-35-L														
ELGG-45	47	45	20	12.5	14.5		22.5	10	20	38		117	57.5	115
ELGG-45-L														
ELGG-55	57	55	30	12.5	14.5		27.5	16	25	48		137	67.5	135
ELGG-55-L														

Size	H4	H5	H6	H7	H8	H9	H10	H11	H12	H13	H14	H15	L1	L2
ELGG-35	19	40	7.5	63	39	21	9.5	15.5	13.5	49	23.5	20	259	89
ELGG-35-L													399	124
ELGG-45	32.5	50	12.5	90	57.5	34.5	14.5	23	21	71	34.5	25	317	108
ELGG-45-L													497	153
ELGG-55	32.5	70	12.5	110	67.5	34.5	14.5	25.5	23.5	86	42	35	361	120
ELGG-55-L													581	175

Size	L3	L4	L5	L6	L7	L8	L9	L10	L11	n	T1	T2	T3
													+0.1
ELGG-35	51	25.5	3	45	76	70	30	20	51	1	3.1	1.6	1.6
ELGG-35-L					146	140		40		2			
ELGG-45	60	30		54	96	90	40	25	60	1	3	1.7	
ELGG-45-L					186	180		50		2			
ELGG-55	62	31		56	116	110	40	35	62	1	4.5	2	
ELGG-55-L					226	220		70		2			



Toothed belt axes ELGG

Ordering data – Modular products

FESTO

Order code


Axis



O top
U underneath
R right
L left
V front
H rear

L Long slide
ZB Additional slide
M Central support

Accessories



NC

MA

NM

SA, SB

SA, SB

EA

Servo motor EMMS-AS
Stepper motor EMMS-ST
→ 18

Axial kit
→ 18

Toothed belt axes ELGG

Ordering data – Modular products

Ordering table								
Size		35	45	55	Conditions	Code	Enter code	
M	Module no.		571058	571059	571060			
	Design		Linear axis				ELGG	ELGG
	Function		Toothed belt				-TB	-TB
O	Guide		Recirculating ball bearing guide					
			Plain-bearing guide				-GF	
M	Size	[mm]	35	45	55	-...	-...	-...
	Stroke length per slide	[mm]	1 ... 700	1 ... 900	1 ... 1,200		-...	-...
	Stroke reserve per slide		0 ... 999 (0 = no stroke reserve)			1	-...H	
O	Slide design		Standard slide					
			Long slide				-L	
	Additional slide		No additional slide					
			1 slide on right, 1 slide on left			2	-ZB	
	Additional function		None					
			Central support			3	-M	
Accessories		Accessories enclosed separately				+	+	
	Proximity sensor (SIES), inductive, T-slot, PNP, incl. switching lug	N/O contact, cable 7.5 m	1 ... 6				...SA	
		N/C contact, cable 7.5 m	1 ... 6				...SB	
	Mounting slot cover		—	1 ... 50 (1 = 2 units, 500 mm)			...NC	
	Slot nut for mounting slot		1 ... 99				...NM	
	Drive shaft		1 ... 4				...EA	
	Profile mounting		1 ... 2				...MA	

[1] The sum of the nominal stroke and 2x stroke reserve must be at least 50 mm and must not exceed the maximum stroke length.

[2] ZB Working stroke reduction → 13

[3] M With the size 35 and stroke > 350 mm, size 45 and stroke > 450 mm, size 55 and stroke > 700 mm, the toothed belt axis is always supplied with central support M.

Size	35		45		55	
Variant	-/L	ZB	-/L	ZB	-/L	ZB
Min. nominal stroke [mm]	50	126	50	146	50	166






Transfer order code

	ELGG	-	TB	-		-		-		-		-		+	
--	------	---	----	---	--	---	--	---	--	---	--	---	--	---	--

Toothed belt axes ELGG

Accessories

FESTO

Permissible axis/motor combinations with axial kit – Without gear unit				
Motor	Axial kit	Axial kit consisting of:		
		Motor flange	Coupling	Coupling housing
				
Type	Part No. Type	Part No. Type	Part No. Type	Part No. Type
ELGG-35				
With servo motor				
EMMS-AS-55-S-...	1133400 EAMM-A-R27-55A	558176 EAMF-A-38A-55A	557999 EAMD-19-15-9-8X10	1133397 EAMK-A-R27-38A
With stepper motor				
EMMS-ST-57-S-...	1133403	560692	561292	1133397
EMMS-ST-57-M-...	EAMM-A-R27-57A	EAMF-A-38A-57A	EAMD-16-15-6.35-8X10	EAMK-A-R27-38A
ELGG-45				
With servo motor				
EMMS-AS-70-S-...	1133401	558018	558000	1133398
EMMS-AS-70-M-...	EAMM-A-R38-70A	EAMF-A-38A-70A	EAMD-25-22-11-10X12	EAMK-A-R38-38A
With stepper motor				
EMMS-ST-87-S-...	1133404	560693	558000	1133398
EMMS-ST-87-M-...	EAMM-A-R38-87A	EAMF-A-38A-87A	EAMD-25-22-11-10X12	EAMK-A-R38-38A
ELGG-55				
With servo motor				
EMMS-AS-100-S-...	1133402 EAMM-A-R48-100A	558020 EAMF-A-48A-100A	558002 EAMD-42-40-19-16X25	1133399 EAMK-A-R48-48A
With stepper motor				
EMMS-ST-87-S-...	1133405	560695	558001	1133399
EMMS-ST-87-M-...	EAMM-A-R48-87A	EAMF-A-48A-87A	EAMD-32-32-11-16X20	EAMK-A-R48-48A
EMMS-ST-87-L-...				

Toothed belt axes ELGG


Accessories

Profile mounting MUE (order code: MA)

Material:
Anodised aluminium
RoHS-compliant

Note

The central support can also be mounted with the profile mounting.



Dimensions and ordering data

For size	B1	B2	B3	D1 Ø	H1	H2	H3	H4
35	51	8	43	3.4	78	6	5.5	2.3
45	69	12	57	5.5	115	10	9	3.2
55	79	12	67	5.5	135	10	9	3.2


For size	H5	L1	L2	L3	L4	Weight [g]	Part No.	Type
35	11	40	20	94	86	20	558042	MUE-50
45	17.5	52	40	139	127	32	562238	MUE-45
55	17.5	52	40	159	147	32	562238	MUE-45

Sensor bracket EAPM-...-SHS, switching lug EAPM-...-SLS (order code SA/SB)

Materials:
Switching lug: Galvanised steel
Sensor bracket: Anodised wrought
aluminium alloy
RoHS-compliant

Note

The sensor bracket can also be mounted on the central support.







Dimensions and ordering data

For size	B1	H1	L1	Weight [g]	Part No.	Type
Sensor bracket						
35, 45, 55	9	6.5	44	20	567537	EAPM-L4-SHS
Switching lug						
35, 45, 55	10	11	57.5	15	567538	EAPM-L4-SLS

Toothed belt axes ELGG



Accessories



FESTO

Ordering data						
	For size	Comment	Order code	Part No.	Type	PU ¹⁾
Drive shaft EAMB						
	35	Alternative interface	EA	558034	EAMB-16-7-8X15-8X10	1
	45			558035	EAMB-18-9-8X16-10X12	
	55			558036	EAMB-24-6-15X21-16X20	
Slot nut NST						
	35	For mounting slot	NM	558045	NST-3-M3	1
	45, 55			150914	NST-5-M5	
Centring sleeve ZBH ²⁾						
	35, 45, 55	For slide	–	186717	ZBH-7	10
Slot cover ABP						
	45, 55	For mounting slot every 0.5 m	NC	151681	ABP-5	2

1) Packaging unit

2) 4 centring sleeves included in the scope of delivery of the axis

Ordering data – Proximity sensors for T-slot, inductive						Technical data → Internet: sies	
	Type of mounting	Electrical connection	Switching output	Cable length [m]	Order code	Part No.	Type
N/O contact							
	Insertable in slot from above, flush with cylinder profile	Cable, 3-wire	PNP	7.5	SA	551386	SIES-8M-PS-24V-K-7,5-OE
		Plug M8x1, 3-pin		0.3	–	551387	SIES-8M-PS-24V-K-0,3-M8D
		Cable, 3-wire	NPN	7.5	–	551396	SIES-8M-NS-24V-K-7,5-OE
		Plug M8x1, 3-pin		0.3	–	551397	SIES-8M-NS-24V-K-0,3-M8D
N/C contact							
	Insertable in slot from above, flush with cylinder profile	Cable, 3-wire	PNP	7.5	SB	551391	SIES-8M-PO-24V-K-7,5-OE
		Plug M8x1, 3-pin		0.3	–	551392	SIES-8M-PO-24V-K-0,3-M8D
		Cable, 3-wire	NPN	7.5	–	551401	SIES-8M-NO-24V-K-7,5-OE
		Plug M8x1, 3-pin		0.3	–	551402	SIES-8M-NO-24V-K-0,3-M8D

Ordering data – Connecting cables				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541333	NEBU-M8G3-K-2.5-LE3
			5	541334	NEBU-M8G3-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541338	NEBU-M8W3-K-2.5-LE3
			5	541341	NEBU-M8W3-K-5-LE3

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support
and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors,
controllers & drives



Pneumatics
Pneumatic linear and rotary actuators,
valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors
and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com