

Stopper cylinders STA/STAF

FESTO



Stopper cylinders STA/STAF

Key features

FESTO

At a glance

- Single-acting or double-acting
- Versions
 - Trunnion
 - Roller
 - Toggle lever
- Direct mounting of solenoid valves on flange plate
- Fast and simple set-up of conveyor lines
- Workpiece carriers, pallets and packages weighing up to 150 kg can be safely stopped
- Gentle stopping without impact vibrations or noise with toggle lever version
- Simple actuation via valve terminal (e.g. in combination with other cylinders at an assembly station)
- Flanged solenoid valve permits fast actuation even over long distances and with individual stopper cylinders
- Space-saving sensing via integrated proximity sensors

Trunnion version



Roller version




Toggle lever version




Mounting options


Through-hole mounting



Direct mounting




Flange mounting




Application options and versions

For heavy masses



Safety



By means of spring return of the piston rod in the event of pressure failure.




Highly effective, low noise level

Toggle lever version with integrated shock absorber facilitates precise and gentle stopping of the workpiece carrier.

Stopper cylinders STA/STAF

Product range overview

FESTO


Function	Version	Type	Piston Ø	Stroke	Type of mounting		Cushioning P	Position sensing A	→ Page/Internet
			[mm]	[mm]	direct	via flange			
Single- or double- acting	Trunnion version								
		STA-...-P-A STAF-...-P-A	20	15	■	–	■	■	4
			32	20	■	■	■	■	
			50	30	■	■	■	■	
	Roller version								
		STA-...-P-A-R STAF-...-P-A-R	20	15	■	–	■	■	10
			32	20	■	■	■	■	
			50	30	■	■	■	■	
			80	30, 40	–	■	■	■	
Toggle lever version									
	STAF-...-P-A-K	32	20	–	■	■	■	20	

Stopper cylinders STA/STAF, trunnion

Functional sequence and type codes

FESTO

Functional sequence




Type codes

STA		20	15	P	A	
Type						
Single-acting or double-acting						
STA	Stopper cylinder					
STAF	Stopper cylinder with flange mounting					
Piston Ø [mm]						
Stroke [mm]						
Cushioning						
P	Flexible cushioning rings/pads at both ends					
Position sensing						
A	Via proximity sensor					
Version						
	Trunnion version					

Stopper cylinders STA/STAF, trunnion

Peripherals overview

FESTO



Accessories		
	Brief description	→ Page/Internet
1	Proximity sensor SME/SMT-8	Can be integrated in the cylinder profile barrel 28
2	Slot cover ABP	For protecting against ingress of dirt 28

Stopper cylinders STA/STAF, trunnion

Technical data

FESTO

Function



Note

Contact with liquids must be avoided during use.

Ø - Diameter
20 ... 50 mm

Stroke length
15 ... 30 mm

www.festo.com



General technical data				
Piston Ø		20	32	50
Pneumatic connection	STA	M5	G¼	G¼
	STAF	–	M5	G¼
Stroke	[mm]	15	20	30
Piston rod Ø	[mm]	12	20	32
Operating pressure	[bar]	10		
Operating medium		Filtered compressed air, lubricated or unlubricated		
Constructional design		Piston cylinder with spring return		
Cushioning		Flexible cushioning rings/pads at both ends		
Position sensing		Via proximity sensor		
Type of mounting	Via through-holes			
	Via female thread			
Mounting position		Any		
Mode of operation		Single-acting or double-acting		
Protection against rotation		None		
Ambient temperature ¹⁾	[°C]	+5 ... +60		


1) Note operating range of proximity sensors.

Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Forces [N]			
Piston Ø	20	32	50
Permissible impact force on the advanced piston rod	260	1,000	2,900
Spring force	13 ... 18	20 ... 42	43 ... 60

Under "impact force" we understand the maximum of a force-time curve during impact/braking of the moveable mass. It is effective vertical to the movement axis of the piston rod. If one regards the elastic components as linear springs, the permitted impact energy can be calculated from the

permitted impact force. This serves for selecting the correct stopper. The stopper must not switch under this force. Depending on the mass to be stopped, it may be advisable to provide an elastic buffer in order to cushion the impact, to reduce noise and to optimize the impact energy.



→ = Direction of impact force


Stopper cylinders STA/STAF, trunnion

Technical data

FESTO


Permissible mass m as a function of the conveyor speed v

The values in the graph opposite are based on the assumption that the workpiece carrier is fitted with a flexible buffer with a deformation path of 1 mm.



Permissible transverse force F_Q during the switching operation as a function of the pressure p

Under "permitted lateral force" during the switching procedure, we understand the force which still exists vertical to the direction of movement of the piston rod after the impact or braking procedure, e.g. by bands still running or the slope power take-off force of an inclined rolling surface. The force is effective statically. The stopper must not switch under this force. In order that the functioning of the cylinder can be guaranteed, a certain minimum pressure must be applied.




Note

Selection aid → 16

Materials

Sectional view



Stopper cylinder		
1	Piston rod	Stainless steel
2	Flange	Die-cast aluminium
3	Cylinder barrel	Anodised aluminium
4	Springs	Spring steel
5	End cap	Anodised aluminium
-	Seals	Polyurethane
-	Note on materials	Free of copper, PTFE and silicone

Stopper cylinders STA/STAF, trunnion


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

Direct mounting



Ø	Stroke	D	D1	D4	D5	E	F	F1	H	H1	H2	L	L1	L2	T	T1
[mm]	[mm]	Ø	Ø													
20	15	12	26	M5	M4	M5	8	45	53	64.5	15	36	22	37.5	4	18
32	20	20	38	M6	M5	G ¹ / ₈	8	56.5	64.5	80.5	20	50	32	52	5	20
50	30	32	53	M8	M6	G ¹ / ₈	8	67.5	75.5	99.5	30	68	50	71	6	20

Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Stopper cylinders STA/STAF, trunnion


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

Flange mounting



Ø	Stroke	B4	D	D2	D3	D6	E1	F2	F3	F4	H2
[mm]	[mm]		Ø	Ø	Ø						
32	20	4.5	20	11	6.6	M3	M5	8.5	14	7	20
50	30	4.5	32	15	9	M4	G ¹ / ₈	9	17	8	30

Ø	Stroke	H6	H10	L	L2	L5	L6	L7	L9	L10	T2	T2
[mm]	[mm]											
32	20	16.5	67.5	50	52	83	32	65	26	16.5	4	6.2
50	30	18	85	68	71	111	45	90	36	7	5	5

• Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Ordering data


Piston Ø [mm]	Stroke [mm]	Direct mounting		Flange mounting	
		Part No.	Type	Part No.	Type
20	15	164 887	STA-20-15-P-A	–	–
32	20	164 888	STA-32-20-P-A	164 890	STAF-32-20-P-A
50	30	164 889	STA-50-30-P-A	164 891	STAF-50-30-P-A

Stopper cylinders STA/STAF, roller

Functional sequence and type codes

FESTO

Functional sequence




Type codes

STA		-	20	-	15	-	P	-	A	-	R
Type											
Single-acting or double-acting											
STA	Stopper cylinder										
STAF	Stopper cylinder with flange mounting										
Piston Ø [mm]											
Stroke [mm]											
Cushioning											
P	Flexible cushioning rings/pads at both ends										
Position sensing											
A	Via proximity sensor										
Version											
R	Roller version										

Stopper cylinders STA/STAF, roller

Peripherals overview

FESTO



Accessories		
	Brief description	→ Page/Internet
1 Proximity sensor SME/SMT-8	Can be integrated in the cylinder profile barrel	28
2 Slot cover ABP	For protecting against ingress of dirt	28

Stopper cylinders STA/STAF, roller

Technical data

FESTO

Function



- Ø - Diameter
20 ... 80 mm

- I - Stroke length
15 ... 40 mm

- T - www.festo.com



Note

Contact with liquids must be avoided during use.



General technical data					
Piston Ø		20	32	50	80
Pneumatic connection	STA	M5	G¼	G¼	–
	STAF	–	M5	G¼	G¼
Stroke	[mm]	15	20	30	30/40
Piston rod Ø	[mm]	12	20	32	50
Operating pressure	[bar]	10			
Operating medium		Filtered compressed air, lubricated or unlubricated			
Constructional design		Piston cylinder with spring return			
Cushioning		Flexible cushioning rings/pads at both ends			
Position sensing		Via proximity sensor			
Type of mounting	Via through-holes				
	Via female thread				
Mounting position		Any			
Mode of operation		Single-acting or double-acting			
Protection against rotation		Flat-sided piston rod			
Ambient temperature ¹⁾	[°C]	+5 ... +60			


1) Note operating range of proximity sensors.

- ¶ - Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Forces [N]					
Piston Ø		20	32	50	80
Stroke		15	20	30	30 40
Permissible impact force on the advanced piston rod		170	830	2,300	14,600 13,300
Spring force		13 ... 18	20 ... 42	43 ... 60	79 ... 115 101 ... 170

Under "impact force" we understand the maximum of a force-time curve during impact/braking of the moveable mass. It is effective vertical to the movement axis of the piston rod. If one regards the elastic components as linear springs, the permitted impact energy can be calculated from the

permitted impact force. This serves for selecting the correct stopper. The stopper must not switch under this force. Depending on the mass to be stopped, it may be advisable to provide an elastic buffer in order to cushion the impact, to reduce noise and to optimize the impact energy.



→ = Direction of impact force


Stopper cylinders STA/STAF, roller

Technical data

FESTO


Permissible mass m as a function of the conveyor speed v

The values in the graph opposite are based on the assumption that the workpiece carrier is fitted with a flexible buffer with a deformation path of 1 mm.



Permissible transverse force F_Q during the switching operation as a function of the pressure p

Under "permitted lateral force" during the switching procedure, we understand the force which still exists vertical to the direction of movement of the piston rod after the impact or braking procedure, e.g. by bands still running or the slope power take-off force of an inclined rolling surface. The force is effective statically. The stopper must not switch under this force. In order that the functioning of the cylinder can be guaranteed, a certain minimum pressure must be applied.




Note

Selection aid → 16

Materials

Sectional view



Stopper cylinder		
1	Roller	Steel
2	Piston rod	Stainless steel
3	Flange	Die-cast aluminium
4	Cylinder barrel	Anodised aluminium
5	Springs	Spring steel
6	End cap	Anodised aluminium
-	Seals	Polyurethane
-	Note on materials	Free of copper, PTFE and silicone

Stopper cylinders STA/STAF, roller


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

Direct mounting



Ø [mm]	Stroke [mm]	B	D Ø	D1 Ø	D4	D5	E	F	F1	H	H1	H3
20	15	4	12	26	M5	M4	M5	8	45	53	64.5	3
32	20	8	20	38	M6	M5	G $\frac{1}{8}$	8	56.5	64.5	80.5	6
50	30	10	32	53	M8	M6	G $\frac{1}{8}$	8	67.5	75.5	99.5	6

Ø [mm]	Stroke [mm]	H4	H5	H9	L	L1	L2	L3	L4	R1	T	T1
20	15	24	15	4	36	22	37.5	2	4.5	5	4	18
32	20	38	20	4	50	32	52	3.5	7.5	9	5	20
50	30	50.5	30	5	68	50	71	7	12	12.5	6	20

• Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Stopper cylinders STA/STAF, roller


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

Flange mounting



Ø [mm]	Stroke [mm]	B	B4	D Ø	D2 Ø	D3 Ø	D6	E1	F2	F3	F4	H3	H4	H5	H6
32	20	8	4.5	20	11	6.6	M3	M5	8.5	14	7	6	38	20	16.5
50	30	10	4.5	32	15	9	M4	G $\frac{1}{8}$	9	17	8	6	50.5	30	18
80	30	18	4.5	50	18	11	M4	G $\frac{1}{8}$	11	17	4.5	10	63	30	22
	40												73	40	

Ø [mm]	Stroke [mm]	H9	H10	L	L2	L3	L4	L5	L6	L7	L9	L10	R1	T2	T3
32	20	4	67.5	50	52	3.5	7.5	83	32	65	26	16.5	9	4	6.2
50	30	5	85	68	71	7	12	111	45	90	36	7	12.5	5	5
80	30	8	119	107	111	11	18	160	63	135	36	18.5	18	6	6
	40		129												

• Note: This product conforms with the ISO 1179-1 standard and the ISO 228-1 standard.

Ordering data

Piston Ø [mm]	Stroke [mm]	Direct mounting		Flange mounting	
		Part No.	Type	Part No.	Type
20	15	164 883	STA-20-15-P-A-R	–	–
32	20	164 884	STA-32-20-P-A-R	164 892	STAF-32-20-P-A-R
50	30	164 885	STA-50-30-P-A-R	164 893	STAF-50-30-P-A-R
80	30	–	–	164 886	STAF-80-30-P-A-R
80	40	–	–	164 894	STAF-80-40-P-A-R

Stopper cylinders STA/STAF


Technical data

FESTO

Selection aid

Stopping a workpiece carrier

The stopper cylinder is used to brake an individual workpiece carrier.



Example

Given:

Friction value $\mu = 0.1$

Delivery speed $v = 10 \text{ m/min}$


Workpiece carrier with workpiece $m = 30 \text{ kg}$

Operating pressure $p = 6 \text{ bar}$

Choice: Stopper cylinder STA...-50-...-R

1. Checking the permissible mass

The maximum permissible mass at a delivery speed of 10 m/min is 60 kg. This means that the total mass of the workpiece carrier and workpiece of 30 kg is permissible.



— STA-20-15-P-A-R
 - - - STA/STAF-32-20-P-A-R
 - · - STA/STAF-50-30-P-A-R
 · · · STA/STAF-80-...-P-A-R

2. Checking the permissible transverse force during the switching operation


Transverse force $F_Q =$ friction force

F_{Friction}

$$\begin{aligned} F_{\text{Friction}} &= \mu \times m \times g \\ &= 0.1 \times 30 \text{ kg} \times 9.81 \text{ m/s}^2 \\ &= \text{approx. } 30 \text{ N} \end{aligned}$$

The maximum permissible transverse force at an operating pressure of 6 bar is 1,100 N.

This means that the transverse force of 30 N is permissible.



— STA-20-15-P-A-R
 - - - STA/STAF-32-20-P-A-R
 - · - STA/STAF-50-30-P-A-R
 · · · STA/STAF-80-30-P-A-R
 - - - STA/STAF-80-40-P-A-R

Stopper cylinders STA/STAF


Technical data

FESTO

Selection aid

Stopping or separating several workpiece carriers

The stopper cylinder is used to separate workpiece carriers. Further workpiece carriers accumulate behind carriers already at the stopper cylinder. It is vital that a buffer is mounted between the workpiece carriers (e.g. elastomer elements).



Example

Given:

Friction value $\mu = 0.1$

Delivery speed $v = 10 \text{ m/min}$

Workpiece carrier with workpiece $m = 30 \text{ kg}$

Operating pressure $p = 6 \text{ bar}$

Maximum number of workpiece carriers accumulating simultaneously $n_{\text{Group}} = 1$

Maximum number of all queued workpiece carriers $n_{\text{Queue}} = 5$


Maximum number of all advancing workpiece carriers $n_{\text{Queue-1}} = 4$

Spring travel of the workpiece carrier buffer $s_F = 1 \text{ mm}$

Choice: Stopper cylinder STA...-50-...-R

1. Checking the permissible mass of the first workpiece carrier

The maximum permissible mass at a delivery speed of 10 m/min is 60 kg . This means that the total mass of the workpiece carrier and workpiece of 30 kg is permissible.



— STA-20-15-P-A-R
 - - - STA/STAF-32-20-P-A-R
 - . - STA/STAF-50-30-P-A-R
 . . . STA/STAF-80-...-P-A-R

2a. Calculation of the maximum permissible impact force when workpiece carriers accumulate behind a carrier at the stopper cylinder

With the STA...-50, the maximum permissible impact force is $2,300 \text{ N}$. This means that with a total force of $1,000 \text{ N}$, the number of workpiece carriers is permissible.

Impact force calculation:

$$F_{\text{Impact}} = \frac{(n_{\text{Group}} \times m) \times v^2}{s_F} = \frac{(1 \times 30\text{kg}) \times (10\text{m}/60\text{s})^2}{0.001\text{m}} = \text{ca. } 850\text{N}$$

Friction force:

$$F_{\text{Friction}} = \mu \times (n_{\text{Queue}} \times m) \times g = 0.1 \times (5 \times 30\text{kg}) \times 9.81\text{m/s}^2 = \text{ca. } 150\text{N}$$

Max. total force:

$$F_{\text{Total force}} = F_{\text{Impact}} + F_{\text{Friction}} = 850\text{N} + 150\text{N} = 1000\text{N}$$

Stopper cylinders STA/STAF

Technical data

FESTO


Selection aid

2b. Checking the permissible transverse force during the switching operation

Transverse force $F_Q =$
friction force F_{Friction}
 $F_{\text{Friction}} = 150 \text{ N}$


The maximum permissible transverse force at an operating pressure of 6 bar is 1,100 N.

This means that the transverse force of 150 N is permissible.




— STA-20-15-P-A-R
- - - STA/STAF-32-20-P-A-R
- · - STA/STAF-50-30-P-A-R
· · · STA/STAF-80-30-P-A-R
- - - STA/STAF-80-40-P-A-R

3. Separating and advancing the workpiece carriers



The maximum permissible mass with the STA...-50-...-R at a delivery speed of 10 m/min is 60 kg.

Since the total mass of the four workpiece carriers advancing on the stopper cylinder is 120 kg, the next largest stopper cylinder must be selected for separating.



— STA-20-15-P-A-R
- - - STA/STAF-32-20-P-A-R
- · - STA/STAF-50-30-P-A-R
· · · STA/STAF-80-30-P-A-R
- - - STA/STAF-80-40-P-A-R

Max. total mass:

$$m_{\text{Total force}} = n_{\text{Queue}-1} \times m = 4 \times 30 \text{ kg} = 120 \text{ kg}$$

Result

The stopper cylinder STA...-80-...-R must be selected for separating five workpiece carriers.

Stopper cylinders STA/STAF

Technical data

FESTO

Application example




Stopper cylinders STAF, toggle lever


Functional sequence

FESTO


Functional sequence



1. Gentle stopping of heavy masses via a hydraulic shock absorber in the piston rod.




2. The toggle lever is locked into the retracted end position so that the workpiece carrier cannot be pushed back by the shock absorber.




3. The workpiece carrier is released by means of compressed air, and the toggle lever is released simultaneously.


X = 62.8 ... 63.4 mm



4. The piston is advanced by means of spring force or compressed air. The toggle lever tips back which prevents the workpiece carrier from being pushed up.



5. The toggle lever is raised by means of spring force and stops the next workpiece carrier.



Protection against rotation:
The guide rod always aligns the toggle lever precisely to the approaching workpiece carrier.



Integrated shock absorber: absorbs impact energy and stops the workpiece carrier gently, and with low noise levels.
The impact energy can be adjusted using the regulating screw in the toggle lever.



Detenting roller lever: the workpiece carrier cannot be pushed back by the shock absorber.



Locking mechanism for disabling the stopper function: the workpiece carrier is able to pass the holding point without activating the cylinder.

Note

Trunnion or roller type stopper cylinders can be mounted in any position.
Stopper cylinders with toggle lever must be mounted in the vertical, upright position.

Stopper cylinders STAF, toggle lever

Key features

FESTO










Mounting options for solenoid valves and valve functions

An MEH, MEBH, MOEH or MOEBH solenoid valve can be mounted on the stopper cylinder for quick, direct actuation of the cylinder. This type of

actuation is only possible for stopper cylinders with flange mounting. The valve must be mounted on the flange

plate via a valve sub-base ZVA. The position of the piston rod when the solenoid valve is in the normal

position depends upon the valve type and the position of the valve on the cylinder.

Application	Piston rod in initial position	Required solenoid valve	Type of mounting for the solenoid valve with sub-base ZVA
	Single-acting		
		Normally advanced 173 125 MEH-3/2-5,0-B 172 999 MEBH-3/2-5,0-B	
		Normally retracted 173 429 MOEH-3/2-5,0-B 173 002 MOEBH-3/2-5,0-B	
	Double-acting		
		Normally advanced 173 128 MEH-5/2-5,0-B 173 005 MEBH-5/2-5,0-B	
		Normally retracted 173 128 MEH-5/2-5,0-B 173 005 MEBH-5/2-5,0-B	



Note

Cylinders are always supplied single-acting with spring. If a double-acting stopper cylinder is required, the filter

nipple in the exhaust port must be removed. The exhaust port is then used as a supply port.

Solenoid valves MEH, MEBH
→ Internet: solenoid valve


Stopper cylinders STAF, toggle lever

Type codes and peripherals overview

FESTO

	STAF	–	32	–	20	–	P	–	A	–	K
Type											
Single-acting or double-acting											
STAF	Stopper cylinder with flange mounting										
Piston Ø [mm]											
Stroke [mm]											
Cushioning											
P	Flexible cushioning rings/pads at both ends										
Position sensing											
A	Via proximity sensor										
Version											
K	Toggle lever version										

Peripherals overview



Accessories		
	Brief description	→ Page/Internet
1	Plug socket with cable KMEB	– kmeb
2	3/2-way valve MEBH	For fast and direct actuation of the stopper cylinder mebh
3	Sub-base ZVA	For stopper cylinder with flange 26
4	Proximity sensor SME/SMT-8	Can be integrated in the cylinder profile barrel 28
5	Slot cover ABP	For protecting against ingress of dirt 28

Stopper cylinders STAF, toggle lever

FESTO

Technical data

Function



- Ø - Diameter
32 mm

- I - Stroke length
20 mm

- T - www.festo.com



Note

Contact with liquids must be avoided during use.




General technical data	
Pneumatic connection	M5
Stroke [mm]	20
Piston rod Ø [mm]	20
Operating pressure [bar]	10
Operating medium	Filtered compressed air, lubricated or unlubricated
Constructional design	Piston cylinder with spring return
Cushioning	Flexible cushioning rings/pads at both ends
Position sensing	Via proximity sensor
Type of mounting	Via through-holes
Mounting position	Vertical, upright
Mode of operation	Single-acting or double-acting
Protection against rotation	Guide rod
Ambient temperature ¹⁾ [°C]	+5 ... +60

1) Note operating range of proximity sensors.

- I - Note: This product conforms to ISO 1179-1 and to ISO 228-1

Forces [N]	
Permissible impact force on the rollers of the toggle lever when the piston rod is advanced and the toggle lever is pushed into its end position	480
Spring force	20 ... 42

Impact force is the basis for the calculation of permissible impact energy. Depending upon the type of load to be stopped, it is advisable to use a flexible buffer to cushion the impact, reduce noise levels and to optimise impact energy.



→ = Direction of impact force


Stopper cylinders STAF, toggle lever

Technical data

FESTO

Permissible mass m as a function of the conveyor speed v

With a friction value of $\mu = 0.1$



Note

The required mass for reliable pushing into the end position is dependent on the friction pairing between the conveyor and conveyed goods, other friction values on request.


Cushioning time is increased for partial loads.
Energy values valid for ambient temperature $T = 20\text{ °C}$.

- Operating range
- Max. workload
- Recommended minimum workload¹⁾
- Required mass²⁾

- 1) For optimum operation of the damper
- 2) Required mass for reliable pushing of the toggle lever into the end position with this friction value

Materials


Sectional view



Stopper cylinder

1	Piston rod	Stainless steel
2	Flange	Die-cast aluminium
3	Cylinder barrel	Anodised aluminium
4	Springs	Spring steel
5	End cap	Anodised aluminium
6	Roller	Polyacetate
-	Seals	Polyurethane
-	Note on materials	Free of copper, PTFE and silicone

Minimum distance to the conveyor



$X = 62.8 \dots 63.4\text{ mm}$

Stopper cylinders STAF, toggle lever


Technical data

FESTO

Dimensions

Download CAD data → www.festo.com

Flange mounting



Ø	B1	B2	B3	B4	D	D2	D3	D6	E1	F2	F3	F4	H6	H7	H8
[mm]					Ø	Ø	Ø								
32	6	18	26	4.5	20	11	6.6	M3	M5	8.5	14	7	16.5	70	9.5

Ø	H10	L	L2	L5	L6	L7	L8	L9	L10	L11	R2	R3	T2	T3
[mm]														
32	67.5	50	52	83	32	65	12	26	16.5	13	7.5	25	4	6.2

• Note: This product conforms to ISO 1179-1 and to ISO 228-1

Ordering data

Piston Ø [mm]	Stroke [mm]	Flange mounting	
		Part No.	Type
32	20	164 880	STAF-32-20-P-A-K

Stopper cylinders STA/STAF

Accessories

FESTO



Sub-base ZVA

for stopper cylinder with flange

Material:

Wrought aluminium alloy

Free of copper, PTFE and silicone



Dimensions and ordering data							
For Ø	B1	B2	B3	D1	CRC ¹⁾	Weight	Part No. Type
[mm]						[g]	
32	56	18	20	G1/8	2	50	164 896 ZVA-1
50/80	57.5	18	20	G1/8	2	52	164 897 ZVA-2

1) Corrosion resistance class 2 as per Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

Stopper cylinders STA/STAF


Accessories

FESTO

Dimensions

Download CAD data → www.festo.com

Mounting dimensions for solenoid valves with sub-base ZVA on stopper cylinders






For Ø [mm]	L	L1	L2	L3	L4	L5	L6
32	55.5	88.5	18.5	51.5	59	35	72
50	65	79	28	42	73	36	71
80	48.5	95.5	11.5	58.5	98	39	68




For Ø [mm]	L7	L8	L9	H1	H2	H3	H4
32	35	72	42	74.5	33.5	48.5	59.5
50	34	73	52	77	31	31	57
80	31	76	71	79	29	53	56



Stopper cylinders STA/STAF

Accessories

FESTO

Ordering data – Proximity sensors for T-slot, magneto-resistive						Technical data → Internet: smt
	Type of mounting	Switch output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above, flush with cylinder profile	PNP	Cable, 3-wire	2.5	543 867	SMT-8M-PS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 866	SMT-8M-PS-24V-K-0,3-M8D
			Plug M12x1, 3-pin	0.3	543 869	SMT-8M-PS-24V-K-0,3-M12
	Insertable in the slot lengthwise, flush with the cylinder profile	PNP	Cable, 3-wire	2.5	543 870	SMT-8M-NS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 871	SMT-8M-NS-24V-K-0,3-M8D
			Cable, 3-wire	2.5	175 436	SMT-8-PS-K-LED-24-B
			Plug M8x1, 3-pin	0.3	175 484	SMT-8-PS-S-LED-24-B
N/C contact						
	Insertable in the slot from above, flush with cylinder profile	PNP	Cable, 3-wire	7.5	543 873	SMT-8M-PO-24V-K7,5-OE

Ordering data – Proximity sensors for T-slot, magnetic reed					Technical data → Internet: sme	
	Type of mounting	Switch output	Electrical connection	Cable length [m]	Part No.	Type
N/O contact						
	Insertable in the slot from above, flush with cylinder profile	Contacting	Cable, 3-wire	2.5	543 862	SME-8M-DS-24V-K-2,5-OE
				5.0	543 863	SME-8M-DS-24V-K-5,0-OE
			Cable, 2-wire	2.5	543 872	SME-8M-ZS-24V-K-2,5-OE
			Plug M8x1, 3-pin	0.3	543 861	SME-8M-DS-24V-K-0,3-M8D
	Insertable in the slot lengthwise, flush with the cylinder profile	Contacting	Cable, 3-wire	2.5	150 855	SME-8-K-LED-24
			Plug M8x1, 3-pin	0.3	150 857	SME-8-S-LED-24
N/C contact						
	Insertable in the slot lengthwise, flush with the cylinder profile	Contacting	Cable, 3-wire	7.5	160 251	SME-8-O-K-LED-24

Ordering data – Connecting cables				Technical data → Internet: nebu	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part No.	Type
	Straight socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 333	NEBU-M8G3-K-2.5-LE3
			5	541 334	NEBU-M8G3-K-5-LE3
	Angled socket, M8x1, 3-pin	Cable, open end, 3-wire	2.5	541 338	NEBU-M8W3-K-2.5-LE3
			5	541 341	NEBU-M8W3-K-5-LE3

Ordering data – Slot cover for T-slot				
	Assembly	Length [m]	Part No.	Type
	Insertable from above	2x 0.5	151 680	ABP-5-S

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788
Phone: 1.631.435.0800; Fax: 1.631.435.8026;
Email: info@festo-usa.com www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4
Phone: 1.905.624.9000; Fax: 1.905.624.9001;
Email: festo.canada@ca.festo.com www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México
Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;
Email: festo.mexico@mx.festo.com www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com