


Guided drives DFME-LAS, electric

FESTO



Guided drives DFME-LAS, electric

Key features

FESTO

At a glance

Characteristics

- The guided drive consists of a freely positionable linear motor, integrated displacement encoder with magnetic strip and reference switch
- Enables positioning with very high dynamic response. Accelerations of up to 80 m/s^2 are possible without load
- Mechanical interfaces are largely compatible with the guided drive DFM-B
- Together with the motor controller SFC-LACI and the associated cables, it is a quickly commissioned positioning system for small loads

Range of applications

- Positioning of small loads such as:
 - placing small parts into and removing small parts from magazines,
 - sorting parts quickly,
 - for equipping and assembly processes

Everything from a single source

Guided drive
DFME-LAS

→ 3



Motor controller
SFC-LACI

→ Internet: sfc-laci

The guided drive DFME-LAS and motor controller SFC-LACI form one unit.

- Thanks to protection class IP54, the SFC can be mounted close to the DFME, either:
 - via central supports or
 - via H-rail
- Just two cables are required between the guided drive DFME and motor controller SFC (motor and encoder cable)
- The motor controller SFC is available with or without control panel
- Up to 31 positioning records

Parameterisation via:

- Control panel:
 - suitable for simple position sequences

Parameterisation via:

- FCT (Festo Configuration Tool) configuration package:
 - via RS 232 interface
 - Windows-based PC user interface, Festo Configuration Tool
- Easy actuation via:
 - I/O interface
 - Profibus
 - CANopen, incl. “interpolated position mode”
 - DeviceNet




CANopen


DeviceNet

Mounting options


Flat from above



Flat from below



Side from below



Guided drives DFME-LAS, electric



Type codes

		DFME	-	32	-	100	-	LAS	-	T	-	H	-	KF	-	S1
Type																
DFME	Guided drive															
Size																
Stroke [mm]																
Drive type/motor technology																
LAS	Linear motor, AC synchronous															
Cable outlet																
T	At the top															
S	At the side															
Cable outlet direction																
H	To the rear															
F	To the front															
L	To the left															
R	To the right															
Guide																
KF	Recirculating ball bearing guide															
Protection class for electrics																
S1	IP65															

Cable outlet direction

With cable outlet at top


With cable outlet at side




Instructions for use

The guided drive with linear motor is not designed for the following sample applications:

- Magnetic field




- Welding application



Guided drives DFME-LAS, electric

Peripherals overview

FESTO




Accessories		
	Brief description	→ Page/Internet
1	Motor controller SFC-LACI	For parameterising and positioning the guided drives sfc-laci
2	Motor/encoder cable NEBM	For connecting the motor and controller sfc-laci
3	Centring sleeve ZBH	For centring loads and attachment components 16

Guided drives DFME-LAS, electric

Technical data

Function




- N- Size
32, 40
- T- Stroke length
100 ... 400 mm

Note

All values are based on a standard temperature of 23 °C.
Dynamic response and accuracy are dependent on the mounting (rigidity) and temperature stresses (heat concentration).

www.festo.com/en/Spare_parts_service



General technical data								
Size		32			40			
Stroke	[mm]	100	200	320	100	200	320	400
Mechanical								
Design		Guided drive						
		Electric linear direct drive						
Guide		Recirculating ball bearing guide						
Drive unit operating mode		Yoke						
Type of mounting		Via female thread and centring sleeve						
		Via through-hole and centring sleeve						
Mounting position		Horizontal						
Stroke reserve	[mm]	3.5						
Continuous feed force ¹⁾	[N]	36	29	29	53	40	49	49
Peak feed force ¹⁾	[N]	94	141	141	183	202	202	202
Max. effective load ²⁾	[kg]	2	6	4	3.4	6	6	6
Max. speed	[m/s]	2	3	3	2	3	3	3
Repetition accuracy	[mm]	±0.015						
Electric								
Type of motor		Linear AC servo motor						
Displacement encoder		Relative measurement, magnetic, incremental, contactless						
Peak motor current	[A]	5.9	16.2	16.2	7.7	22.4	22.4	22.4
Nominal motor current	[A]	2.2	3.3	3.3	2.2	4.4	5.4	5.4
Rated motor output	[W]	108	87	87	159	120	147	147
Homing		Integrated reference sensor						

1) Disregarding friction

2) Limited by motor power. The values specified here are recommended values

Operating and environmental conditions		
Ambient temperature	[°C]	0 ... +40
Max. motor temperature	[°C]	70 (warning at 70 °C, shut-off at 75 °C)
Standard temperature ¹⁾	[°C]	23
Temperature monitoring		Shuts off if motor overheats
Protection class (mechanical system)		IP40
Protection class (electrical connection)		IP40 (with DFME-...-S1: IP65)
CE marking (see declaration of conformity)		To EU EMC Directive

1) Unless otherwise stated, all values are based on standard temperature

Guided drives DFME-LAS, electric


Technical data

FESTO

Weight [g]							
Size	32			40			
Stroke [mm]	100	200	320	100	200	320	400
Product weight	4,100	4,900	5,600	6,300	7,000	8,200	8,600
Moving load	1,030	1,280	1,500	1,620	2,060	2,290	2,520

Materials


Sectional view



Guided drive		
1	Yoke plate	Anodised wrought aluminium alloy
2	Housing	Anodised wrought aluminium alloy
3	Guide rod	Tempered steel (surface hardened)
4	Cooling tube	Anodised wrought aluminium alloy
5	Piston rod	High-alloy stainless steel
–	Terminal strip	Die-cast zinc
–	Screws	Steel
–	Note on materials	Contains PWIS (paint-wetting impairment substances) RoHS-compliant

Stroke reserve and cushioning length

- 1 Working stroke:**
The recommended, available operating range
- L12 Stroke reserve:**
The distance from the end positions of the working stroke to the buffers
- L10, L11 Cushioning length:**
The distance from the buffer surface to the mechanical end position



Size		Retracted		Advanced	
		L12	L10	L12	L11
32	[mm]	1.75	1.5	1.75	2
40	[mm]	1.75	1.5	1.75	2


Guided drives DFME-LAS, electric

Technical data

FESTO

Dynamic characteristic load values

Torques are indicated with reference to the centre of the yoke plate.
These values must not be exceeded during dynamic operation.
Special attention must be paid to the cushioning phase.



If the drive is simultaneously subjected to several of the indicated forces and torques, the following equation must be satisfied in addition to the indicated maximum loads:


$$\frac{|F_{y1}|}{F_{y\max.}} + \frac{|F_{z1}|}{F_{z\max.}} + \frac{|M_{x1}|}{M_{x\max.}} + \frac{|M_{y1}|}{M_{y\max.}} + \frac{|M_{z1}|}{M_{z\max.}} \leq 1$$

Permissible forces and torques								
Size	32				40			
Stroke [mm]	100	200	320		100	200	320	400
F _y max., F _z max [N]	20	60	40		34	60	60	60
M _x max. [Nm]	5	4	3		6.3	5.3	4.3	3.3
M _y max. [Nm]	2	12	12		3.4	12	19	24
M _z max. [Nm]	2	12	12		3.4	12	19	24

Note


PositioningDrives
sizing software
→ www.festo.com

Piston rod displacement f, with fully advanced piston rod, as a function of stroke l




— 2 kg
- - - 4 kg
- · - 6 kg

DFME-32



DFME-40




Guided drives DFME-LAS, electric

Technical data


FESTO

Positioning time t as a function of stroke l , effective load M and duty cycle ED


DFME-32-100



DFME-32-200



DFME-32-320




Guided drives DFME-LAS, electric

Technical data

FESTO


Positioning time t as a function of stroke l , effective load M and duty cycle ED

DFME-40-100




- M 1.0 kg, ED 25% to 50%
- - - M 1.7 kg, ED 25% to 50%
- M 3.4 kg, ED 25%
- - - M 3.4 kg, ED 50%

DFME-40-200




- M 1.0 kg, ED 25%
- - - M 1.0 kg, ED 50%
- M 3.0 kg, ED 25%
- - - M 3.0 kg, ED 50%
- - - M 6.0 kg, ED 25%
- - - M 6.0 kg, ED 50%

DFME-40-320



- M 1.0 kg, ED 25%
- - - M 1.0 kg, ED 50%
- M 3.0 kg, ED 25%
- - - M 3.0 kg, ED 50%
- - - M 6.0 kg, ED 25%
- - - M 6.0 kg, ED 50%

DFME-40-400



- M 1.0 kg, ED 25%
- - - M 1.0 kg, ED 50%
- M 3.0 kg, ED 25%
- - - M 3.0 kg, ED 50%
- - - M 6.0 kg, ED 25%
- - - M 6.0 kg, ED 50%

Guided drives DFME-LAS, electric

Technical data

FESTO

Feed force F as a function of stroke l

The graphs are based on practical values with friction taken into account.


Peak feed force

—


Continuous feed force
at ambient temperature:

----- from 23 °C
—— from 30 °C
----- from 40 °C


DFME-32-100




DFME-32-200




DFME-32-320




DFME-40-100




DFME-40-200



DFME-40-320



DFME-40-400



Guided drives DFME-LAS, electric

Technical data

Feed force F as a function of speed v


The graphs are based on practical values under the following conditions:

- Stroke centre of the electric cylinder
- Friction taken into account


- Standard temperature of 23 °C
- Max. motor temperature of 70 °C

- Peak feed force
- Continuous feed force


DFME-32-100




DFME-32-200




DFME-32-320




DFME-40-100




DFME-40-200



DFME-40-320




DFME-40-400



Technical data

Download CAD Data → www.festo.com/us/cad



Guided drives DFME-LAS, electric

Technical data

Size	B1	B2	B3	B4 ¹⁾	B5	B6	B7 ¹⁾	B8	B9 ¹⁾	B10	B11	B12
32	110	108	109	45	7	33.5	43	35	40	16	78	15
40	120	118	119	46	6.5	34.5	51	35	50	16	88	15

Size	B13	B14	B15 ¹⁾	B16	B17	B18	B19	B20	B21	B22	B23	B27
32	78	41	26	31.6	34.5	43	55	76	38	8	30.5	20
40	88	41	36	33	36.6	45	60	76	39	8	30.5	20

Size	B28	B29	D1	D2 Ø	D3 Ø H7	D4	D5 Ø H7	D6	D7 Ø	D8 Ø	D9 Ø	D10
32	42.6	21.8	M8	11	12	M6	9	M6	16	10.5	50	M5
40	42.6	21.8	M8	11	12	M8	9	M6	16	10.5	50	M5

Size	D11 Ø	D12 Ø	D13 Ø	D14 Ø	EE1	EE2	H1	H2	H3	H4	H5 ¹⁾	H6
32	13.3	47	45	8	M5	M7	49	47	77.3	6	37	24.5
40	13.3	52	50.5	8	M5	M7	54	52	82.8	6	42	27

Size	H7	H8 ¹⁾	H9	H10	H11	H14	H15	H16	H17	H18	H19	H20
32	8.5	30	21	52.9	6.5	64.3	57.9	43	20	24.5	41.6	19
40	10	30	26	59.5	8	70.8	62.7	48.5	20	27	46	19

Size	L2	L3	L4	L8	L9 ¹⁾	L10	L11 ¹⁾	L12	L13	L14 ¹⁾	L15	L16
			-1.75			-1.75						
32	197.5	14	16	29	40	45	80	7	82	14	40.5	36.5
40	227.5	14	16	29	40	45	120	7	85	11.5	42.7	38.5

Size	L18	L19	L20	L21	n	T1	T2	T3	T4	T5	T6	T7	T8
								+0.1		+0.1			
32	151.5	227	96.8	25	1	20	6.8	2.6	11	2.1	8	9	8
40	181.5	257	96.8	25	2	20	6.8	2.6	16	2.1	12	9	10

Size	Stroke [mm]	L1	L5	L6	L7	L17
		-1.75				
32	100	349	135.5	18	17.7	87.5
	200	449	235.5	118	117.7	187.5
	320	569	355.5	238	237.7	307.5
40	100	423.5	180	18	16.7	127.8
	200	523.5	280	118	116.7	227.8
	320	643.5	400	238	236.7	347.8
	400	723.5	480	318	316.7	427.8

1) Tolerance for centring hole ± 0.02 mm
Tolerance for threaded hole ± 0.1 mm

Guided drives DFME-LAS, electric


Technical data

FESTO

Dimensions

Download CAD Data → www.festo.com/us/cad

DFME-...S – Cable outlet at side



Size	B24	B25	B26	H12	H13
32	11.3	33	143	55	56.5
40	11.3	33	153	61.5	63

Guided drives DFME-LAS, electric

Ordering data – Modular products

Ordering table					
Size	32	40	Conditions	Code	Enter code
[M] Module No.	562828	562829			
Function	Guided drive			DFME	DFME
Size	32	40		-...	
Stroke [mm]	100	100		-...	
	200	200			
	320	320			
	-	400			
Drive type	Linear motor			-L	-L
Motor technology	AC synchronous			AS	AS
Cable outlet	At the top			-T	
	At the side			-S	
Cable outlet direction	To the rear			-H	
	To the front			-F	
	To the left			-L	
	To the right			-R	
Guide	Recirculating ball bearing guide			-KF	-KF
[O] Protection class for electrics	IP65			-S1	

Transfer order code

DFME - - - **L** **AS** - - - **KF** -

Guided drives DFME-LAS, electric


Accessories

FESTO

Centring sleeve ZBH

Material:

High-alloy steel



Dimensions and ordering data							
B1	D1	D2	CRC ¹⁾	Weight	Part No.	Type	PU ²⁾
-0.2	Ø h7	Ø		[g]			
4	9	6.4	2	1	150927	ZBH-9	10
5	12	10.3	2	1	189653	ZBH-12	10

1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents

2) Packaging unit quantity

Product Range and Company Overview

A Complete Suite of Automation Services

Our experienced engineers provide complete support at every stage of your development process, including: conceptualization, analysis, engineering, design, assembly, documentation, validation, and production.



Custom Automation Components
Complete custom engineered solutions



Custom Control Cabinets
Comprehensive engineering support and on-site services



Complete Systems
Shipment, stocking and storage services

The Broadest Range of Automation Components

With a comprehensive line of more than 30,000 automation components, Festo is capable of solving the most complex automation requirements.



Electromechanical
Electromechanical actuators, motors, controllers & drives



Pneumatics
Pneumatic linear and rotary actuators, valves, and air supply



PLCs and I/O Devices
PLC's, operator interfaces, sensors and I/O devices

Supporting Advanced Automation... As No One Else Can!

Festo is a leading global manufacturer of pneumatic and electromechanical systems, components and controls for industrial automation, with more than 12,000 employees in 56 national headquarters serving more than 180 countries. For more than 80 years, Festo has continuously elevated the state of manufacturing with innovations and optimized motion control solutions that deliver higher performing, more profitable automated manufacturing and processing equipment. Our dedication to the advancement of automation extends beyond technology to the education and development of current and future automation and robotics designers with simulation tools, teaching programs, and on-site services.

Quality Assurance, ISO 9001 and ISO 14001 Certifications

Festo Corporation is committed to supply all Festo products and services that will meet or exceed our customers' requirements in product quality, delivery, customer service and satisfaction.

To meet this commitment, we strive to ensure a consistent, integrated, and systematic approach to management that will meet or exceed the requirements of the ISO 9001 standard for Quality Management and the ISO 14001 standard for Environmental Management.



© Copyright 2008, Festo Corporation. While every effort is made to ensure that all dimensions and specifications are correct, Festo cannot guarantee that publications are completely free of any error, in particular typing or printing errors. Accordingly, Festo cannot be held responsible for the same. For Liability and Warranty conditions, refer to our "Terms and Conditions of Sale", available from your local Festo office. All rights reserved. No part of this publication may be reproduced, distributed, or transmitted in any form or by any means, electronic, mechanical, photocopying or otherwise, without the prior written permission of Festo. All technical data subject to change according to technical update.



Printed on recycled paper at New Horizon Graphic, Inc., FSC certified as an environmentally friendly printing plant.

Festo North America

Festo Regional Contact Center

5300 Explorer Drive
Mississauga, Ontario L4W 5G4
Canada

USA Customers:

For ordering assistance,

Call: 1.800.99.FESTO (1.800.993.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: customer.service@us.festo.com

For technical support,

Call: 1.866.GO.FESTO (1.866.463.3786)

Fax: 1.800.96.FESTO (1.800.963.3786)

Email: product.support@us.festo.com

Canadian Customers:

Call: 1.877.GO.FESTO (1.877.463.3786)

Fax: 1.877.FX.FESTO (1.877.393.3786)

Email: festo.canada@ca.festo.com

USA Headquarters

Festo Corporation
395 Moreland Road
P.O. Box 18023
Hauppauge, NY 11788, USA
www.festo.com/us

USA Sales Offices

Appleton

North 922 Tower View Drive, Suite N
Greenville, WI 54942, USA

Boston

120 Presidential Way, Suite 330
Woburn, MA 01801, USA

Chicago

1441 East Business Center Drive
Mt. Prospect, IL 60056, USA

Dallas

1825 Lakeway Drive, Suite 600
Lewisville, TX 75057, USA

Detroit – Automotive Engineering Center

2601 Cambridge Court, Suite 320
Auburn Hills, MI 48326, USA

New York

395 Moreland Road
Hauppauge, NY 11788, USA

Silicon Valley

4935 Southfront Road, Suite F
Livermore, CA 94550, USA

United States



USA Headquarters, East: Festo Corp., 395 Moreland Road, Hauppauge, NY 11788

Phone: 1.631.435.0800; Fax: 1.631.435.8026;

Email: info@festo-usa.com

www.festo.com/us

Canada



Headquarters: Festo Inc., 5300 Explorer Drive, Mississauga, Ontario L4W 5G4

Phone: 1.905.624.9000; Fax: 1.905.624.9001;

Email: festo.canada@ca.festo.com

www.festo.ca

Mexico



Headquarters: Festo Pneumatic, S.A., Av. Ceylán 3, Col. Tequesquahuac,
54020 Tlalneapantla, Edo. de México

Phone: 011 52 [55] 53 21 66 00; Fax: 011 52 [55] 53 21 66 65;

Email: festo.mexico@mx.festo.com

www.festo.com/mx

Central USA

Festo Corporation
1441 East Business
Center Drive
Mt. Prospect, IL 60056, USA
Phone: 1.847.759.2600
Fax: 1.847.768.9480



Western USA

Festo Corporation
4935 Southfront Road,
Suite F
Livermore, CA 94550, USA
Phone: 1.925.371.1099
Fax: 1.925.245.1286



Festo Worldwide

Argentina Australia Austria Belarus Belgium Brazil Bulgaria Canada Chile China Colombia Croatia Czech Republic Denmark
Estonia Finland France Germany Great Britain Greece Hong Kong Hungary India Indonesia Iran Ireland Israel Italy Japan Latvia
Lithuania Malaysia Mexico Netherlands New Zealand Norway Peru Philippines Poland Romania Russia Serbia Singapore
Slovakia Slovenia South Africa South Korea Spain Sweden Switzerland Taiwan Thailand Turkey Ukraine United States Venezuela

www.festo.com