

Linear drives DGCI, with displacement encoder

FESTO



Cylinders with displacement encoder

Product range overview

FESTO

Function	Type	Brief description
Drives	Rodless	
	DDLI	 • Without guide • With contactless displacement encoder • Based on linear drive DGC-K • Supply ports optionally on end face or front • System product for handling and assembly technology
	DGCI	 • With guide • With contactless displacement encoder • Based on linear drive DGC • Supply ports optionally on end face or front • System product for handling and assembly technology
	DGPI/DGPIL	 Do not use for new projects! • With or without guide • With contactless displacement encoder, integrated • Wide range of options for mounting on drives • System product for handling and assembly technology
	DGP/DGPL	 Do not use for new projects! • With or without guide • With potentiometer or contactless displacement encoder, attached • With clamping unit • Wide range of options for mounting on drives
	With piston rod	
	DNCI	 • With contactless displacement encoder • Various piston rod variants • Standards-based cylinder to ISO 15552   
	DDPC	 • With contactless displacement encoder • Various piston rod variants • Standards-based cylinder to ISO 15552   
	DNC/DSBC	 • With attached potentiometer MLO-LWG • Various piston rod variants • Standards-based cylinder to ISO 15552   
Swivel module	Swivel module	
	DSMI	 • Based on swivel module DSM • Integrated rotary encoder • Compact design • Wide range of mounting options

Cylinders with displacement encoder

Product range overview

FESTO

Piston Ø	Stroke/swivel angle [mm/°]	Suitable				
		For positioning with		For end-position controller		For use as a measuring cylinder
		CPX-CMAX	SPC200	CPX-CMPX	SPC11	
Rodless						
25, 32	100; 160; 225; 300; 360; 450; 500; 600; 750; 850; 1,000; 1,250; 1,500; 1,750; 2,000	■	■	■	■	■
18, 25, 32, 40, 63	100; 160; 225; 300; 360; 450; 500; 600; 750; 850; 1,000; 1,250; 1,500; 1,750; 2,000	■	■	■	■	■
25, 32, 40, 50, 63	225; 300; 360; 450; 500; 600; 750; 1,000; 1,250; 1,500; 1,750; 2,000	■	■	■	■	■
25, 32, 40, 50, 63	225; 300; 360; 450; 500; 600; 750; 1,000; 1,250; 1,500; 1,750; 2,000	–	■	–	■	■
With piston rod						
32, 40, 50, 63	10 ... 2,000	–	–	–	–	■
	100 ... 750	■	■	■	■	–
80, 100	10 ... 2,000	–	–	–	–	■
	100 ... 750	■	■	■	■	–
32, 40, 50, 63, 80	100, 150, 225, 300, 360, 450, 600, 750	■	■	■	■	■
Swivel module						
25, 40, 63	270	■	■	■	■	■

Cylinders with displacement encoder

Key features

FESTO


Servopneumatic drive technology

Positioning and Soft Stop applications as an integral component of the valve terminal CPX – the modular peripheral system for decentralised automation tasks.

The modular design means that valves, digital inputs and outputs, positioning modules and end-position controllers, as appropriate to the application, can be combined in almost any way on the CPX terminal.

Advantages:

- Pneumatics and electrics – control and positioning on one platform
- Innovative positioning technology – piston rod drives, rodless drives, rotary drives
- Actuation via fieldbus
- Remote maintenance, remote diagnostics, web server, SMS and e-mail alert are all possible via TCP/IP
- Modules can be quickly exchanged and expanded without altering the wiring



Axis controller CPX-CMAX



Free choice:

Position and force control, directly actuated or selected from one of 64 configurable position sets. If you are looking for something more: the configurable function for switching to the next set enables simple functional sequences to be realised in the axis controller CPX-CMAX.

All stations are recognised as the auto-identification function identifies each station with its device data on the controller CPX-CMAX.

Also included:

The functional scope of the controller CPX-CMAX includes actuation of a brake or clamping unit via the proportional directional control valve VPWP.

Up to 8 modules (max. 8 axes) can be operated in parallel and independently of each other. Commissioning via FCT (Festo configuration software) or via fieldbus: no programming, only configuration.

Technical data → Internet: cpx-cmax

Advantages:

- Greater flexibility
- OEM friendly – commissioning also via fieldbus
- Easy installation and fast commissioning
- Cost-effective
- You program the system in your PLC environment

Cylinders with displacement encoder

Key features

FESTO

End-position controller CPX-CMPX



Fast travel between the mechanical end stops of the cylinder, stopping gently and without impact in the end position.
Fast commissioning via control panel, fieldbus or handheld unit. Improved downtime control.
Actuation of a brake or clamping unit via the proportional directional control valve VPWP is an integral part of the controller CMPX.

Depending on the fieldbus chosen, up to 9 end-position controllers can be actuated on the CPX terminal. All system data can be read and written via the fieldbus, including, for example, the mid positions.

Technical data → Internet: [cpx-cmpx](#)

Advantages:

- Greater flexibility
- OEM friendly – commissioning also via fieldbus
- Easy installation and fast commissioning
- Cost-effective
 - Up to 30% faster cycle rates
 - Significantly reduced system vibration
- Improved work ergonomics thanks to significantly reduced noise level
- The extended diagnostics help to reduce the service time for the machine

Proportional directional control valve VPWP



The 5/3-way proportional directional control valve for applications with Soft Stop and pneumatic positioning.
Fully digitalised – with integrated pressure sensors, with new diagnostic functions.
In sizes 4, 6, 8 and 10.
Flow rate of 350, 700, 1,400 and 2,000 l/min.

With switching output for actuating a brake.
Coloured supply ports.
Pre-assembled cables guarantee faultless and fast connection with the controllers CPX-CMPX and CPX-CMAX.

Technical data → Internet: [vpwp](#)

Advantages:

- Easy installation and fast commissioning
- Reduction of system downtimes thanks to the new diagnostic options
- With switching output for actuating a brake/clamping unit

Measuring module CPX-CMIX



Fully digital data acquisition and transmission means pneumatic cylinders can be used as sensors. With very high repetition accuracy and incorporating both analogue and digital measuring sensors.

Suitable for the linear drive DGCI with displacement encoder for measuring absolute values, for the piston rod drive DNCI/DDPC with incremental displacement encoder or even for a potentiometer of the type MLO.

Technical data → Internet: [cpx-cmix](#)

Advantages:

- All process steps can be documented, which improves quality
- An adjustable contact force (via pressure regulator) increases the precision of the "displacement sensor"
- With displacement encoders for measuring absolute values, the actual position is immediately available after the system is switched on


Cylinders with displacement encoder

Drive options

FESTO

System with linear drive DDLI, DGCI

Technical data → Internet: dgci



- 1 Controller module CPX-CMPX or CPX-CMAX
- 2 Proportional directional control valve VPWP
- 3 Linear drive DDLI, DGCI with displacement encoder
- 6 Connecting cable KVI-CP-3-...


- Pneumatic rodless linear drive with displacement encoder, with or without recirculating ball bearing guide
- Displacement encoder with absolute and contactless measuring
- Identical design to pneumatic linear drive DGC
- Diameter: 18 ... 40 and 63 mm
- Stroke: 100 ... 2,000 mm in fixed lengths
- Range of applications: Soft Stop and pneumatic positioning
- Loads from 1 ... 180 kg
- No sensor interface required

Advantages:

- Complete drive unit
- DDLI for easy connection to customer's guide system
- Excellent running characteristics
- For fast and accurate positioning down to ± 0.2 mm (only with axis controller CPX-CMAX)

System with linear drive DGPI, DGPII or displacement encoder MME-MTS

Technical data → Internet: dgpi



- 1 Controller module CPX-CMPX or CPX-CMAX
- 2 Proportional directional control valve VPWP
- 3 Linear drive DGPI, DGPII with displacement encoder
- 6 Connecting cable KVI-CP-3-...
- 9 NEBP-M16W6-K-2-M9W5


- Pneumatic rodless linear drive with displacement encoder, with or without recirculating ball bearing guide
- Displacement encoder with absolute and contactless measuring
- Diameter: 25 ... 63 mm
- Stroke: 225 ... 2,000 mm in fixed lengths
- Range of applications: Soft Stop and pneumatic positioning
- Loads from 2 ... 180 kg
- No sensor interface required

Advantages:

- Complete drive unit
- DGPI for easy connection to customer's guide system
- Excellent running characteristics
- For fast and accurate positioning down to ± 0.2 mm (only with axis controller CPX-CMAX)

System with standard cylinder DNCI, DDPC

Technical data → Internet: dnci



- 1 Controller module CPX-CMPX or CPX-CMAX
- 2 Proportional directional control valve VPWP
- 3 Standard cylinder DNCI, DDPC with displacement encoder
- 5 Sensor interface CASM-S-D3-R7
- 6 Connecting cable KVI-CP-3-...

- Standard cylinder with integrated displacement encoder, conforms to DIN ISO 6432, VDMA 24 562, NF E 49 003.1 and Uni 10 290
- Displacement encoder with contactless and incremental measuring
- Diameter: 32 ... 100 mm
- Stroke: 100 ... 750 mm
- Range of applications: Soft Stop and pneumatic positioning
- Loads from 3 ... 450 kg and a matching sensor interface CASM-S-D3-R7
- Pre-assembled cables guarantee faultless and fast electrical connection

Advantages:

- Compact drive unit
- Can be used universally
- Also with guide unit
- For fast and accurate positioning down to ± 0.5 mm (only with axis controller CPX-CMAX)


Cylinders with displacement encoder

Drive options

FESTO

System with swivel module DSMI

Technical data → Internet: [dsmi](#)



- 1 Controller module CPX-CMPX or CPX-CMAX
- 2 Proportional directional control valve VPWP
- 3 Swivel module DSMI with displacement encoder
- 4 Sensor interface CASM-S-D2-R3
- 6 Connecting cable KVI-CP-3-...
- 7 Connecting cable NEBC-P1W4-K-0,3-N-M12G5


- Swivel module DSMI with integrated displacement encoder
- Identical design to pneumatic swivel module DSM
- Absolute displacement encoder on basis of potentiometer
- Swivel range from 0 ... 270°
- Size: 25, 40, 63
- Max. torque: 5 ... 40 Nm
- Range of applications: Soft Stop and pneumatic positioning
- Mass moments of inertia from 15 ... 6,000 kgcm² and a matching sensor interface CASM-S-D2-R3
- Pre-assembled cables guarantee faultless and fast connection with the proportional directional control valve VPWP

Advantages:

- Complete drive unit, compact, can be used immediately
- High angular acceleration
- With adjustable fixed stops
- For fast and accurate positioning down to ±0.2° (only with axis controller CPX-CMAX)

System with potentiometer

Technical data → Internet: [casm](#)



- 1 Controller module CPX-CMPX or CPX-CMAX
- 2 Proportional directional control valve VPWP
- 4 Sensor interface CASM-S-D2-R3
- 6 Connecting cable KVI-CP-3-...
- 7 Connecting cable NEBC-P1W4-K-0,3-N-M12G5
- 8 Connecting cable NEBC-A1W3-K-0,4-N-M12G5

- Attachable potentiometers with absolute measurement, with high degree of protection
- With connecting rod or moment compensator
- Measuring range: 100 ... 2,000 mm
- Pre-assembled cables guarantee faultless and fast connection with the sensor interface CASM
- Range of applications: Soft Stop and pneumatic positioning with cylinder Ø 25 ... 80 mm, e.g. DNC or DSBC
- Loads from 1 ... 300 kg

Advantages:

- Easy installation and fast commissioning
- Cost-effective
- Can also be used in harsh environmental conditions
- Variety of drives: CPX-CMPX and CPX-CMAX also support cylinders with external displacement encoder

Cylinders with displacement encoder

Drive options

FESTO

System components for Soft Stop systems with end-position controller CPX-CMPX							
3	Linear drive		Standard cylinder	Swivel module	Displacement encoder		→ Page/ Internet
	DDL/DGCI	DGPI	DNCI, DDPC	DSMI	MLO-LWG/-TLF	MME-MTS	
1	End-position controller CPX-CMPX	■	■	■	■	■	cmpx
2	Prop. directional control valve VPWP	■	■	■	■	■	vpwp
4	Sensor interface CASM-S-D2-R3	–	–	■	■	–	casm
5	Sensor interface CASM-S-D3-R7	–	–	■	–	–	casm
6	Connecting cable KVI-CP-3-...	■	■	■	■	■	kvi
7	Connecting cable NEBC-P1W4-...	–	–	■	■ / –	–	nebc
8	Connecting cable NEBC-A1W3-...	–	–	–	– / ■	–	nebc
9	Connecting cable NEBP-M16W6-...	–	■	–	–	■	nebp

System components for pneumatic positioning systems with axis controller CPX-CMAX							
3	Linear drive		Standard cylinder	Swivel module	Displacement encoder		→ Page/ Internet
	DDL/DGCI	DGPI	DNCI, DDPC	DSMI	MLO-LWG/-TLF	MME-MTS	
1	Axis controller CPX-CMAX	■	■	■	■	■	cmax
2	Prop. directional control valve VPWP	■	■	■	■	■	vpwp
4	Sensor interface CASM-S-D2-R3	–	–	■	■	–	casm
5	Sensor interface CASM-S-D3-R7	–	–	■	–	–	casm
6	Connecting cable KVI-CP-3-...	■	■	■	■	■	kvi
7	Connecting cable NEBC-P1W4-...	–	–	■	■ / –	–	nebc
8	Connecting cable NEBC-A1W3-...	–	–	–	– / ■	–	nebc
9	Connecting cable NEBP-M16W6-...	–	■	–	–	■	nebp

System components for measuring cylinders with measuring module CPX-CMIX							
	Linear drive		Standard cylinder	Swivel module	Displacement encoder		→ Page/ Internet
	DDL/DGCI	DGPI	DNCI, DDPC	DSMI	MLO-LWG/-TLF	MME-MTS	
Measuring module CPX-CMIX-M1-1	■	■	■	■	■	■	cmix
Sensor interface CASM-S-D2-R3	–	–	–	■	■	–	casm
Sensor interface CASM-S-D3-R7	–	–	■	–	–	–	casm
Connecting cable KVI-CP-3-...	(■)	(■)	■	■	■	(■)	kvi
Connecting cable NEBC-P1W4-...	–	–	–	■	■ / –	–	nebc
Connecting cable NEBC-A1W3-...	–	–	–	–	– / ■	–	nebc
Connecting cable NEBP-M16W6-...	–	■	–	–	–	■	nebp

Cylinders with displacement encoder


Overview

FESTO

Individual components for positioning


With axis controller SPC200

→ Internet: [spc200](#)



With end-position controller SPC11


→ Internet: [spc11](#)



Individual components for use as a measuring cylinder

With measuring module CPX-CMIX

→ Internet: [cmix](#)




Linear drives DGCI, with displacement encoder

Key features

FESTO

At a glance



1 Displacement encoder → 18

- High degree of protection IP67
- Non-contacting
- Measures absolute values

2 Supply ports → 35

- Optionally on two sides (on the end face or at the front)
- Optionally with different coloured push-in fittings for simple and error-free tubing connections

3 End stops → 24

- Metal fixed stop
- Shock absorber, precisely adjustable

4 Profile mounting → 22

- Profile mountings remain on the base plate after the drive is dismantled. This saves time during assembly and removal

5 Recirculating ball bearing guide → 16

- Piston Ø 18 ... 63 mm
- Stroke lengths 100 ... 2,000 mm
- Guide backlash = 0 mm
- For medium and large loads
- Precision mounting interface with stainless steel slide
- Operating behaviour under torque load = very good

6 Recirculating ball bearing guide with protected guide → 16

- Piston Ø 18 ... 40 mm
- Stroke lengths 100 ... 2,000 mm
- Guide backlash = 0 mm
- The protected guide cleans the guide rail and protects the recirculating ball bearing guide by means of an additional wiper seal and lubrication unit

– Passive guide axis DGC-FA → dgc-fa

- Without drive
- Piston Ø 8 ... 63 mm
- Stroke lengths 1 ... 5,000 mm
- Guide backlash = 0 mm
- Precision guide, suitable for DGCI. Can be used as a machine component or as a twin guide with DGCI

– Passive guide axis with protected guide DGC-FA-GP → dgc-fa


- Without drive
- Piston Ø 18 ... 63 mm
- Stroke lengths 1 ... 5,000 mm
- Guide backlash = 0 mm
- The protected guide cleans the guide rail and protects the recirculating ball bearing guide by means of an additional wiper seal and lubrication unit

Linear drives DGCI, with displacement encoder

Key features

Options

Central lubrication




The lubrication adapter enables the guide of the linear drive DGCI to be permanently lubricated in applications in humid or wet ambient conditions using semi or fully automatic relubrication devices.

The adapters are suitable for oils and greases.

- For piston Ø 25, 32, 40, 63 mm
- Connections:
 - On both sides of the slide
 - In three places (front, top, rear) on each side

Technical data → 23

Clamping unit – 1H-PN




- 1-channel design, for holding loads
- Reliable holding is guaranteed since the forces act directly on the slide
- A limited number of emergency braking operations are permissible with the size 40
- No stroke reduction; the drive is extended by the length of the clamping unit

- For piston Ø 25, 32, 40 mm

Technical data → 21

Additional slide – KL/KR



- Additional slide, either to the right or left of the main slide
- To increase the torques

- For piston Ø 18, 25, 32, 40, 63 mm

Technical data → 34

NSF-H1 lubricant for the food industry

The linear drive is of limited suitability for the food industry. More information on suitability for use in the food industry → Manufacturer's declaration.

Not approved for use in the food industry:


- DGCI-...-GP (protected version)
- DGCI-... with integrated shock absorbers

Linear drives DGCI, with displacement encoder

Peripherals overview

FESTO

-  - Note
Drive must not be operated without end stops or shock absorbers.



Linear drives DGCI, with displacement encoder

Peripherals overview

Variants and accessories			
Type	For piston Ø	Brief description	→ Page/Internet
1 Linear drive DGCI-KF	18 ... 63	Linear drive without accessories, with recirculating ball bearing guide.	16
2 Slot cover L	18 ... 63	For protecting against the ingress of dirt and securing proximity sensor cables.	44
3 Intermediate position module DADM-DGC	25, 32	Facilitates intermediate positions with metal fixed stop. The module can be attached.	42
4 Shock absorber retainer DADP-DGC	18 ... 63	For variable end-position adjustment in combination with the stop KYC.	40
5 Centring pin/sleeve ¹⁾ ZBS/ZBH	18 ... 63	For centring loads and attachments on the slide.	44
6 Clamping unit 1H-PN	25, 32, 40	For holding loads.	21
7 Stop KYC	18 ... 63	For variable end-position adjustment in combination with the shock absorber retainer DADP-DGC.	40
8 Shock absorber YSR	18 ... 63	Self-adjusting hydraulic shock absorber with spring return and linear cushioning characteristics.	36
9 Shock absorber YSRW	18 ... 63	Self-adjusting hydraulic shock absorber with spring return and progressive cushioning characteristics.	36
10 Push-in fitting QS	18 ... 63	For connecting compressed air tubing with standard O.D.	35
11 Profile mounting M	18 ... 63	Simple and precise mounting option via dovetail connection.	39
12 Slot nut B	25 ... 63	For mounting attachments.	44
13 Centring pin/sleeve ¹⁾ ZBS/ZBH	18 ... 63	For centring the drive without foot mountings (user-specific).	44
14 Foot mounting F	18 ... 63	For mounting on the end cap.	38
– Proportional directional control valve VPWP	18 ... 63	Regulates the compressed air and therefore the position of the slide.	44

1) Included in the scope of delivery of the drive

 Note
Allocation table of drives and
associated proportional directional
control valves → 44

Type codes

14

Linear drives DGCI, with displacement encoder

FESTO

Type codes




		ZUB	F		2B	
Accessories						
ZUB	Accessories enclosed separately					
Type of mounting						
F	Foot mounting					
M	Profile mounting					
Slot cover						
...L	For sensor slot					
Slot nut						
...B	For mounting slot					
Operating instructions						
0	Express waiver – no operating instructions to be included					

Linear drives DGCI, with displacement encoder

FESTO

Technical data

Function



www.festo.com



- Ø - Diameter
18 ... 63 mm
- | - Stroke length
100 ... 2,000 mm

General technical data					
Piston Ø	18	25	32	40	63
Design	Rodless linear drive with displacement encoder				
Mode of operation	Double-acting				
Moment compensator principle	Slotted cylinder, mechanically coupled				
Guide	External recirculating ball bearing guide				
Mounting position	Any				
Type of mounting	Profile mounting				
	Foot mounting				
	Direct mounting				
Cushioning → 21	Via metal fixed stop				
	Via shock absorber, self-adjusting at both ends				
Position sensing	Via attached displacement encoder				
Measuring principle (displacement encoder)	Digital, magnetostrictive, non-contacting and absolute measurement				
Pneumatic connection ¹⁾	M5	G1/8		G1/4	G3/8
Stroke ²⁾	[mm]	100; 160; 225; 300; 360; 450; 500; 600; 750; 850; 1,000; 1,250; 1,500; 1,750; 2,000			
Protected version		Optional			–
Max. speed ³⁾	[m/s]	5			
Stroke tolerance	[mm]	0 ... 2.5			

- 1) Recommended push-in fittings → 44
With pre-assembled push-in fittings, the tubing diameters apply → 22
- 2) Note stroke reduction in combination with CPX-CMAX, SPC200
- 3) Only applies to applications with end-position controller CPX-CMPX, SPC11 and axis controller CPX-CMAX, SPC200. Otherwise a maximum speed of 3 m/s is permitted.

Operating and environmental conditions					
Piston Ø	18	25	32	40	63
Operating pressure	[bar]	2 ... 8			1.5 ... 8
Operating pressure ¹⁾	[bar]	4 ... 8			
Operating medium ²⁾	Compressed air according to ISO 8573-1:2010 [6:4:4]				
Note about the operating/pilot medium	Lubricated operation not possible				
	Pressure dew point 10 °C below ambient/medium temperature				
Ambient temperature	[°C]	-10 ... +60			
Vibration resistance to DIN/IEC 68, Part 2-6	At 10 ... 58 Hz: 0.15 mm				
	At 58 ... 150 Hz: 2G				
Continuous shock resistance to DIN/IEC 68, Part 2-27	Half sine 15 g, 11 ms				
CE mark (see declaration of conformity) ³⁾	To EU EMC Directive				
Certification	C-Tick				
Corrosion resistance class CRC ⁴⁾	1				
ATEX	Specified types → www.festo.com				

- 1) Only applies to applications with end-position controller CPX-CMPX, SPC11 and axis controller CPX-CMAX, SPC200
- 2) The proportional directional control valve VPWP, MPYE requires these characteristic values
- 3) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com → Support → User documentation.
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.
- 4) Corrosion resistance class 1 according to Festo standard 940 070
Components subject to low corrosion stress. Transport and storage protection. Parts that do not have primarily decorative surface requirements, e.g. in internal areas that are not visible or behind covers.

Linear drives DGCI, with displacement encoder

FESTO

Technical data

Forces [N] and impact energy [Nm]					
Piston Ø	18	25	32	40	63
Theoretical force at 6 bar	153	295	483	754	1,870
Impact energy in the end positions					
With fixed stop	0.4	0.5	0.7	0.7	0.7
With shock absorber YSR/YSRW	→ 21				

Positioning characteristics with axis controller CPX-CMAX, SPC200					
Piston Ø	18	25	32	40	63
Mounting position	Any				
Resolution [mm]	0.01				
Repetition accuracy [mm]	→ 19				
Minimum load, horizontal ¹⁾ [kg]	1	2	3	5	12
Maximum load, horizontal ¹⁾ [kg]	15	30	50	75	180
Minimum load, vertical ¹⁾ [kg]	1	2	3	5	12
Maximum load, vertical ¹⁾ [kg]	5	10	15	25	60
Minimum travel speed [m/s]	0.05				
Maximum travel speed [m/s]	5				
Typical positioning time, long stroke ²⁾ [s]	0.75/1.15	0.65/1.00	0.65/1.05	0.70/1.05	1.05/1.20
Typical positioning time, short stroke ³⁾ [s]	0.38/0.65	0.38/0.60	0.38/0.60	0.38/0.60	0.65/0.65
Minimum positioning stroke ⁴⁾ [%]	≤ 3				
Stroke reduction ⁵⁾ [mm]	20	25	25	35	35
Recommended proportional directional control valve					
For CPX-CMAX	→ 44				
For SPC200	→ 46				

- 1) Load = effective load + mass of all moving parts on the drive
- 2) At 6 bar, horizontal mounting position, DGCI-XX-1000, 800 mm travel at min./max. load
- 3) At 6 bar, horizontal mounting position, DGCI-XX-1000, 100 mm travel at min./max. load
- 4) Referred to the maximum stroke of the drive, but never more than 20 mm
- 5) The stroke reduction is to be maintained on each side of the drive, the max. positionable stroke is therefore: stroke – 2x stroke reduction

Force control characteristics with axis controller CPX-CMAX					
Piston Ø	18	25	32	40	63
Mounting position	Any				
Maximum controllable force ¹⁾ [N]	138	266	435	679	1,683
Typical friction forces ²⁾ [N]	40	60	40	50	70
Repetition accuracy of pressure control ³⁾⁴⁾ [%]	< ±2				

- 1) Advancing/retracting at 6 bar
- 2) These values can fluctuate greatly from cylinder to cylinder and are not guaranteed. These friction forces must also be taken into consideration when using an external guide or when the cylinder is moving other components subject to friction
- 3) This value defines the repetition accuracy with which the internal differential pressure in the cylinder is controlled and refers to the maximum controllable force (the internal differential pressure corresponds to the prescribed force setpoint value)
- 4) The effective force at the workpiece and its accuracy depends largely on the friction in the system as well as the repetition accuracy of the internal control system. Note that friction forces always work against the direction of movement of the piston. The following formula can be used as a rule of thumb for the force F at the workpiece:

$$F = F_{\text{setpoint}} \pm F_{\text{friction forces}} \pm \text{repetition accuracy of pressure control}$$

Linear drives DGCI, with displacement encoder

FESTO

Technical data

Positioning characteristics with Soft Stop end-position controller CPX-CMPX, SPC11						
Piston Ø		18	25	32	40	63
Mounting position		Any				
Repetition accuracy ¹⁾	[mm]	±2				
Minimum load, horizontal ²⁾	[kg]	1	2	3	5	12
Maximum load, horizontal ²⁾	[kg]	15	30	50	75	180
Minimum load, vertical ²⁾	[kg]	1	2	3	5	12
Maximum load, vertical ²⁾	[kg]	5	10	15	25	60
Travel time	[s]	➔ SoftStop sizing software: ➔ www.festo.com				
Recommended proportional directional control valve						
For CPX-CMPX		➔ 45				
For SPC11		➔ 46				

1) One intermediate position. The accuracy in the end positions depends solely on the design of the end stops


2) Load = effective load + mass of all moving parts on the drive

Electrical data – Displacement encoder	
Output signal	Digital
Linearity error ¹⁾	[%] < ±0.02, min. ±50 µm
Maximum travel speed	[m/s] 5
Protection class	IP67
CE marking (see declaration of conformity)	To EU EMC Directive ²⁾
Power supply	[V DC] 24 (±25%)
Current consumption	[mA] Typically 100
Maximum temperature coefficient	[ppm/°K] 15
Electrical connection	Cable with 5-pin plug, round type M9
Cable length	[m] 1.5
Cable quality	Suitable for use with energy chains

1) Always refers to max. stroke

2) For information about the applicability of the component see the manufacturer's EC declaration of conformity at: www.festo.com → Support → User documentation.
If the component is subject to restrictions on usage in residential, office or commercial environments or small businesses, further measures to reduce the emitted interference may be necessary.

Pin allocation of plug



Pin	Function
1	24 V
2	–
3	0 V

Pin	Function
4	CAN_H
5	CAN_L
–	Screened

Linear drives DGCI, with displacement encoder


FESTO

Technical data

Weight [g]					
Piston Ø	18	25	32	40	63
DGCI-...					
Basic weight with 0 mm stroke	1,200	2,400	3,100	7,300	22,500
Additional weight per 10 mm stroke	38	56	81	124	243
Moving load	360	770	1,170	2,360	8,200
Moving load on additional slide	300	650	950	2,000	5,600
DGCI-...-1H-PN – With clamping unit					
Basic weight with 0 mm stroke	–	3,436	4,582	12,386	–
Additional weight per 10 mm stroke	–	0.056	0.081	0.124	–
Moving load	–	1,430	2,084	5,519	–


Materials

Sectional view



Linear drives	
1 Guide rail	High-alloy steel
2 Slide	High-alloy steel
3 End cap	Anodised aluminium
4 Cylinder profile, housing	Anodised aluminium
– Seals, sealing band	Polyurethane
– Guide band, dirt wiper, reversing roller	Polyacetal
– Cover	Polyacetal, polyamide, powder-coated aluminium
– Displacement encoder	Anodised aluminium, glass-fibre reinforced polyphthalamide
– Cable	Polyurethane
– Note on materials	Free of copper and PTFE

Repetition accuracy x as a function of stroke l



Linear drives DGCI, with displacement encoder


Technical data

FESTO


Characteristic load values for linear drive with recirculating ball bearing guide and guide

The indicated forces and torques refer to the slide surface and the centre of the slide.

These values must not be exceeded during dynamic operation. Special attention must be paid to the deceleration phase.



GP – Protected guide



If the drive is simultaneously subjected to several of the forces and torques listed below, the following equation must be satisfied in addition to the indicated maximum loads:

$$\frac{F_y}{F_{y_{max.}}} + \frac{F_z}{F_{z_{max.}}} + \frac{M_x}{M_{x_{max.}}} + \frac{M_y}{M_{y_{max.}}} + \frac{M_z}{M_{z_{max.}}} \leq 1$$

Permissible forces and torques						
Piston Ø	18	25	32	40	63	
F _{y_{max.}} [N]	1,850	3,050	3,310	6,890	15,200	
F _{z_{max.}} [N]	1,850	3,050	3,310	6,890	15,200	
M _{x_{max.}} [Nm]	16	36	54	144	529	
M _{y_{max.}} [Nm]	51	97	150	380	1,157	
M _{z_{max.}} [Nm]	51	97	150	380	1,157	

- - Note

To avoid distortion in the slide, the bearing surfaces of the attachments must maintain a flatness of 0.01 mm.


Linear drives DGCI, with displacement encoder

Technical data

FESTO



Maximum permissible piston speed with shock absorber v as a function of effective load m

Piston $\varnothing$ 18 ... 63 with YSR cushioning



— $\varnothing$ 18 - - - $\varnothing$ 40
 - · - $\varnothing$ 25 - · - $\varnothing$ 63
 - - - $\varnothing$ 32

Piston $\varnothing$ 18 ... 63 with YSRW cushioning




Note

This data represents the maximum values that can be achieved. In practice, values fluctuate relative to the size of the effective load.

Technical data – Clamping unit			Dimensions → 32
Size	25	32	40
Pneumatic connection	M3	M5	M5
Clamping type	Clamping via spring force, released via compressed air		
Static holding force [N]	320	500	1,200
Max. number of emergency braking operations ¹⁾ at reference energy [Nm]	–	–	750 35
Number of clamping operations under nominal load [million switching cycles]	0.45	0.55	0.05

1) Emergency braking refers to braking the effective load if the drive axis loses power.

Operating and environmental conditions – Clamping unit	
Operating medium	Compressed air according to ISO 8573-1:2010 [7:4:4]
Operating pressure	
Clamping unit opened [bar]	4.5 ... 8
Clamping unit closed [bar]	Pressureless
Ambient temperature [°C]	–10 ... +60



Note

No stroke reduction in combination with the clamping unit; the drive is extended by the length of the clamping unit.



Linear drives DGCI, with displacement encoder

FESTO

Technical data

Number of profile mountings MUC as a function of overall length

Excessive distances between the profile mountings can reduce the positioning accuracy. The following table shows the required minimum number of profile and foot mountings.

Stroke [mm]	Number of mounting attachments		
	Order code M		Order code F
	Profile mounting	Foot mounting	+ profile mounting
			
100 ... 400	2	2	0
401 ... 600	2	2	1
601 ... 1,200	3	2	1
1,201 ... 1,400	3	2	2
1,401 ... 2,000	4	2	2

Tubing diameter with pre-assembled push-in fittings					
Size	Stroke [mm]	Ø in [mm]			
		6	8	10	12
DGCI-18	100 ... 2,000	■	–	–	–
DGCI-25	100 ... 160	■	–	–	–
	225 ... 2,000	–	■	–	–
DGCI-32	100 ... 2,000	–	■	–	–
DGCI-40	100 ... 750	–	■	–	–
	850 ... 2,000	–	–	■	–
DGCI-63	100 ... 300	–	■	–	–
	360 ... 750	–	–	■	–
	850 ... 2,000	–	–	–	■

Linear drives DGCI, with displacement encoder

FESTO

Technical data

Central lubrication

The lubrication adapter enables the guide of the linear drive DGCI to be permanently lubricated in applications in humid or wet ambient conditions using semi or fully automatic relubrication devices.


- For piston $\varnothing$ 25, 32, 40, 63
- The modules are suitable for oils and greases
- The dimensions of the linear drive DGCI are the same with and without central lubrication modules
- Both lubrication adapters must be connected
- There are three connection options on each side
- Can be used in combination with:
 - Standard slide GK
 - Additional slide KL, KR
- Cannot be used in combination with:
 - Protected recirculating ball bearing guide GP

Slide dimensions
→ 30


Order code C in the modular product system → 37

Connection options

Only the connection at the rear or on the top can be used in combination with shock absorbers in the end caps.




Only the connection on the front or top can be used in combination with shock absorber retainer DADP.



Connection option for customer design

The drawing opposite shows the connection option on the top lubrication interface using a customer design.



- D1 8^{+0.2} mm
D2 6 mm
T1 0.6^{-0.05} mm
T2 0.1^{+0.2} mm
O-ring $\varnothing$ 6x1 mm (DIN3771)

- 1 Slot depth for O-ring
2 Required air gap


Additional dimensions → 30

Structure of a central lubrication system

A central lubrication system requires various additional components. The illustration shows different options (using a hand pump, pneumatic container pump or electric container pump) required as a minimum for designing a central lubrication system. Festo does not sell these additional components; however, they can be obtained from the following companies:

- Lincoln
- Bielomatik
- SKF (Vogel)

Festo recommends these companies because they can supply all the necessary components.




- 1 Hand pump
2 Pneumatic container pump
3 Electric container pump
4 Manually operated container pump
5 Nipple block
6 Distributor block
7 Tubing or piping
8 Fittings


Technical data

Technical drawing of a linear actuator assembly. The drawing shows a side view of the actuator with various dimensions and labels. Key dimensions include L8, L3, L7, L10+, L1+, L2, L5, L6, L9, L4, J1, J2, J3, D1, D2, D3, H5, H3, T1, T2, T3, and 26. Labels include B, A, C, EE, 1, 2, 7, and 26. The drawing is a detailed technical illustration of the actuator's components and their relative positions.

Ø 18 ... 40



Ø 18



- | | | | |
|--|--|---------------------------------------|--------------------------------|
| + plus stroke length | 2 Supply port options on 2 sides, for supply port at one end (on the end face or at the front) | 4 Mounting hole for foot mounting HPC | 6 Hole for centring sleeve ZBH |
| 1 Supply port options on 2 sides (on the end face or at the front) | | 5 Hole for centring pin ZBS | 7 Additional slide |
| | | | 8 Thread for end stop |

Linear drives DGCI, with displacement encoder

FESTO

Technical data

∅ [mm]	B1	B2	B3	B4 ±0.1	B5 ±0.05	B6	B7	B8 ±0.1	B9	B10	B11	B12
18	44.5	49.9	19.5	8.8	21	31	–	3.8	1	2.4	5.5	15.5
25	59.8	66	30	12.65	30	42	1	6.65	1	3.5	9.3	21
32	73	79	38.5	5.7	63.1	57.5	–	8.5	1.5	14	14.9	18
40	91	98.5	45	17.2	55	65	–	12.2	2	8	16.5	24.8
63	142	149	68	–	–	97	–	19.5	5	15.5	21	30

∅ [mm]	B13	B14 ±0.05	B15	B16	D1 ∅	D2	D3 ∅ H7	D4	EE	H1	H2	H3
18	39	19.5	68.3	0.8	2±0.05	M4	5	M12x1	M5	56.3	23.1	55
25	53	29	82.4	–	3±0.05	M5	9	M16x1	G1/8	68	29	67
32	65	38.5	97.8	–	3±0.05	M6	9	M16x1	G1/8	78.5	30	77
40	80.5	45	110.3	–	4±0.05	M6	9	M22x1.5	G1/4	99.5	41.5	97.5
63	123.5	68	146.3	–	9 ^{H7}	M10	9	M26x1.5	G3/8	153.5	48.5	151

∅ [mm]	H4 ±0.1	H5	H6	H7	H8	H9	H10	H11	H12 ±0.05	H13	H14	J1	J2	J3
18	9.6	13.4	20	4.6	2.4	25.2	46	8.5±0.15	30	20	2.3	20	16.5	11
25	13.65	15.8	24	7.65	4.5	29	55.5	12±0.15	35	20	4.7	26.1	18.6	17
32	5.7	17	27.7	8.5	14	35.2	63.8	11.45±0.15	50	20	5.9	30	22	18.5
40	17.2	25	36.5	12.2	8	44	81.5	15±0.15	60	20	13.9	35	26	26
63	68	34.8	46	19.5	–	67	131	15.5±0.2	120	20	23.7	41.5	39.5	31.5

∅ [mm]	L1			L2			L3	L4	L5	L6	L7		
	KF	KF-GP	1H-PN	KF	KF-GP	1H-PN					KF	KF-GP	KF-YSR(W)
18	150	157	–	74.5	78	–	5.7	5.8	15	5.5	14.5 ... 16.5	18 ... 20	14.5 ... 34.5
25	200	205	271	100	102.5	100	10.5	10.6	24.5	10.6	22.5 ... 26.5	25 ... 29	22.5 ... 47.5
32	250	250	320.5	124.8	124.8	124.8	14.5	14.5	30.5	14.5	27.3 ... 32.3	27.3 ... 32.3	27.3 ... 52.3
40	300	312	458	150	156	150	14.6	14.6	33.5	14.6	31 ... 36	37 ... 42	31 ... 56
63	400	–	–	200	–	–	20	20	44	20	41 ... 46	–	41 ... 76

∅ [mm]	L8		L9		L10 max.	T1	T2	T3 +0.2	T6	Stroke tolerance
	YSR	YSRW	KF ±0.2	KF-GP ±0.2						
18	29.9	32.6	–	3.5	119	9	2	3.1	15	0 ... 2.5
25	35.6	38.6	16.5	19	119	17.5	2	2.1	17.3	
32	19.5	28	35.3	35.3	119	15	2	2.1	20	
40	38.5	43.5	17	23	119	20	2	2.1	25.7	
63	38.3	48.3	97	–	119	27.5	2.1 ^{+0.2}	2.1	36.1	

-  - Note

For reasons of functional safety of the displacement encoder and stability of the linear drive DGCI, the distance L7 must not fall below the values in the table.

Linear drives DGCI, with displacement encoder

Technical data


FESTO

Dimensions


Download CAD data → www.festo.com

Slide


Ø 18




View A




Ø 25




View A




Ø 32




View A



Ø 40



View A



- [5] Hole for centring sleeve ZBH
- [6] Hole for centring pin ZBS

Linear drives DGCI, with displacement encoder

Technical data


FESTO

Dimensions


Download CAD data → www.festo.com

Slide

Ø 63



View A



5 Hole for centring sleeve ZBH

6 Hole for centring pin ZBS

Ø	B3	D1	D2 Ø H7	D3	D4	D5 Ø H7	H2	H3	H4 ±0.03	H5 ±0.1	L1
[mm]	±0.05										
18	4.5	M5	5	–	M5	5	16.5	–	–	18	88±0.1
25	5	M5	9	M6	M5	7	22	32±0.2	–	25.5	104±0.2
32	5	M5	9	M6	M5	7	19.5	47±0.2	20	29.5	131±0.2
40	7	M5	9	M6	M6	7	26.8	55±0.2	20	34.7	169±0.2
63	8	M8	9	M6	M8	9	55	90±0.3	40	–	256±0.1

Ø	L2	L3	L4 ±0.03	L5 ±0.1	L6 ±0.05	L7 ±0.1	L8	T1	T2	T3	T4
[mm]	±0.2										
18	–	20±0.1	20	10	–	–	99	–	3.1±0.1	7.5	6.7
25	74	44±0.2	40	30	60	–	118.5	10	2.1±0.2	7.5	8
32	100	70±0.2	40	45	85	–	145.7	10	2.1±0.2	7.5	8
40	116	76±0.2	40	60	110	–	195.4	10.5	2.1±0.2	7.5	8.5
63	169	99±0.2	40	70	130	190	280	15.5	2.1±0.2	18	13.6

Linear drives DGCI, with displacement encoder

Technical data


FESTO

Dimensions



Download CAD data → www.festo.com

Slide, variant GP – Protected recirculating ball bearing guide


Ø 18





View A




Ø 25





View A




Ø 32





View A



Ø 40



View A



5 Hole for centring sleeve ZBH

6 Hole for centring pin ZBS

Linear drives DGCI, with displacement encoder

FESTO

Technical data

Ø [mm]	B3 ±0.05	D1	D2 Ø H7	D3	D4	D5 Ø H7	H2	H3
18	4.5	M5	5	–	M5	5	16.5	–
25	5	M5	9	M6	M5	7	22	32±0.2
32	5	M5	9	M6	M5	7	19.5	47±0.2
40	7	M5	9	M6	M6	7	26.8	55±0.2

Ø [mm]	H4 ±0.03	H5 ±0.1	L1	L2 ±0.2	L3	L4 ±0.03	L5 ±0.1	L6 ±0.05
18	–	18	88±0.1	–	20±0.1	20	10	–
25	–	25.5	104±0.2	74	44±0.2	40	30	60
32	20	29.5	131±0.2	100	70±0.2	40	45	85
40	20	34.7	169±0.2	116	76±0.2	40	60	110

Ø [mm]	L8	L9	T1	T2	T3	T4
18	99	120	–	3.1±0.1	7.5	6.7
25	118.5	144	10	2.1±0.2	7.5	8
32	145.7	173	10	2.1±0.2	7.5	8
40	195.4	231	10.5	2.1±0.2	7.5	8.5

Linear drives DGCI, with displacement encoder

Technical data


FESTO

Dimensions


Download CAD data → www.festo.com

Slide, variant C – Lubrication adapter


Ø 25




View A




Ø 32




View A




Ø 40




View A



Ø 63



View A



5 Hole for centring sleeve ZBH

Linear drives DGCI, with displacement encoder

FESTO


Technical data

Ø	B3	B5	B6	D1	D2 Ø H7	D3	D4	D5 Ø H7	D6	H2	H3	H4	H5
[mm]	±0.05	±0.05										±0.03	±0.1
25	5	1	8.5	M5	9	M6	M5	7	M6x1	22	32±0.2	–	25.5
32	5	1.5	7.5	M5	9	M6	M5	7	M6x1	19.5	47±0.2	20	29.5
40	7	18.2	18.2	M5	9	M6	M6	7	M6x1	26.8	55±0.2	20	34.7
63	8	12.5	27.5	M8	9	M6	M8	9	M6x1	55	90±0.3	40	–


Ø	L1	L2	L3	L4	L5	L6	L7	L8	L10	T1	T2	T3	T4
[mm]		±0.2	±0.2	±0.03	±0.1	±0.05	±0.1				+0.2		
25	104±0.2	74	44	40	30	60	–	145	132	10	2.1	7.5	8
32	131±0.2	100	70	40	45	85	–	172	158	10	2.1	7.5	8
40	169±0.2	116	76	40	60	110	–	223	209	10.5	2.1	7.5	8.5
63	256±0.1	169	99	40	70	130	190	308.4	293.8	15.5	2.1	18	13.6

Profile barrel


Ø 18




Ø 25




Ø 32



Ø 40



Ø 63



- 1 Sensor slot for proximity sensor
- 2 Mounting slot for slot nut

Ø [mm]	B10	B11	H10	H11
25	15.23	–	–	–
32	18	–	26.5	–
40	20.5	40	20.5	20
63	49	30	37	30

Linear drives DGCI, with displacement encoder

Technical data


FESTO

Dimensions

Download CAD data → www.festo.com

1H – With clamping unit

Size 25/32



Note

Total length L1 with stroke = 0 mm → 25

In case of subsequent installation/modification, note that the dimension H1 is bigger on a linear drive with clamping unit.

- 1 Supply port
- 2 Lubrication adapter

Type	B1	B2	B3	B4	H1	H2	H3	D1	D2	L2	L3	L4	L5	L6
DGCI-25-...-1H-PN	83.6	64.9	17.6	47.5	79	21	39.5	M6	M3	100	182.3	63	198	–
DGCI-25-...-C-1H-PN														193.8
DGCI-32-...-1H-PN	99.9	79.9	20.9	59	88.5	20	41.5	M6	M5	124.8	209.4	62	223.9	–
DGCI-32-...-C-1H-PN														221

Linear drives DGCI, with displacement encoder

Technical data


FESTO

Dimensions

Download CAD data → www.festo.com

1H – With clamping unit

Size 40



 Note

Total length L1 with stroke = 0 mm → 25

In case of subsequent installation/modification, note that the dimension

H1 is bigger on a linear drive with clamping unit.

 Supply port

 Lubrication adapter

Type	B1	B2	B3	B4	H1	H2	H3	D1	D2	L2	L3	L4	L6
DGCI-40-...-1H-PN	109.9	97	11.7	69.4	113.5	28	48.9	M6	M5	150	331.2	105	–
DGCI-40-...-C-1H-PN													345.7

Linear drives DGCI, with displacement encoder

Ordering data – Modular products


FESTO

Order code

Mandatory data/options


-  - Note

Drive must not be operated without end stops or shock absorbers.



Effective stroke reduction when ordering an additional slide KL or KR

For a linear drive DGCI with additional slide, the effective stroke is reduced by the length of the additional slide and the distance between both slides.



Given:

DGCI-18-500-...

L = 20 mm

L17 = 99 mm

The effective stroke is reduced to

381 mm = 500 mm – 20 mm – 99 mm

Ø [mm]	L17	
	DGCI-...-KF	DGCI-...-KF-...-GP
18	99	120
25	118.5	144
32	145.7	173
40	195.4	231
63	280	–

Linear drives DGCI, with displacement encoder

FESTO

Ordering data – Modular product

Order code – Alternative supply port


Four different supply port options (see below) can be selected when ordering the linear drive.

To make commissioning easier, the linear drive is supplied with different


coloured push-in fittings (black or blue release ring) and without push-in

fittings in the case of the variant DGCI-...Q.


Push-in fitting at both ends, front (standard)
DGCI-...



Push-in fitting at both ends, end face
DGCI-...-QD




Push-in fitting at one end, end face
DGCI-...-QR



- - Note
Compressed air supply at one end is only recommended for strokes up to 600 mm.

No push-in fitting, end face open
DGCI-...Q



Direction of movement of the slide:

S To the right:

Fitting with black release ring

B To the left:

Fitting with blue release ring


Alternative port option

K Supply ports open

A Supply ports sealed


Order code

KL/KR – With additional slide



GP – With protected recirculating ball bearing guide

- - Note
In the case of the variant with GP, only fixed stops may be used in the end caps. Shock absorbers may only be used in combination with the shock absorber retainer DADP-DGC.



Linear drives DGCI, with displacement encoder

FESTO

Ordering data – Modular product

Ordering table								
Size	18	25	32	40	63	Condi- tions	Code	Enter code
M Module No.	544425	544426	544427	544428	544429			
Function	Linear drive with displacement encoder						DGCI	DGCI
Piston Ø [mm]	18	25	32	40	63		*...	
Stroke [mm]	100; 160; 225; 300; 360; 450; 500; 600; 750; 850; 1,000; 1,250; 1,500; 1,750; 2,000						*...	
Guide	Recirculating ball bearing guide						-KF	-KF
O Alternative supply port	Push-in fitting at both ends, front face (standard)							
	Push-in fitting at both ends, end face						-QD	
	Push-in fitting at one end, end face, right side					1	-QR	
	Threaded connection (end face open, front face sealed)						-Q	
↓	M5	G $\frac{1}{8}$	G $\frac{1}{8}$	G $\frac{1}{4}$	G $\frac{3}{8}$			

1 QR

Only for stroke 100 ... 600 mm

Transfer order code

	DGCI	-		-		-	KF	-	
--	------	---	--	---	--	---	----	---	--

FESTO

Ordering table									
Size	18	25	32	40	63	Condi- tions	Code	Enter code	
Slide	Protected recirculating ball bearing guide					–	2	-GP	
Lubrication	Standard								
	Lubrication approved for use in food applications						3	-H1	
	Standard								
	– Lubrication adapter							-C	
	Additional slide, standard, on left						4	-KL	
	Additional slide, standard, on right						4	-KR	
	–		None			–			
	–		1-channel			–	5	-1H	
	–		None			–			
	–		Pneumatically actuated			–	5	-PN	
	Adjustable mechanical stop without cushioning (standard)								
	Shock absorber, self-adjusting							-YSR	
	Shock absorber, self-adjusting, progressive							-YSRW	
	Accessories							ZUB-	ZUB-
	Type of mounting	Foot mounting (includes 0 ... 2 profile mountings depending on the stroke)						7	F
Profile mounting (2 ... 4 depending on the stroke)						7	M		
Slot cover for sensor slot	1 ... 9							...L	
Slot nut for mounting slot	–		1 ... 9					...B	
User documentation	Express waiver - no operating instructions to be included (already available) (operating instructions in PDF format are available free of charge on our website at http://www.festo.com)							O	

- 7 F, M** Allocation table → 22

- - - - - - - - - - **ZUB** - - - -

Linear drives DGCI, with displacement encoder

Accessories

FESTO


Foot mounting HPC
(order code: F)

Material:
Galvanised steel



Note

Additional profile mountings MUC
are required for strokes above
400 mm → 22.



Dimensions and ordering data

| For Ø | AB
Ø | AC | AO | AT | AU | B1 | B2 | B3 |
|-------|---------|----|------|----|-------|-------|------|-------|
| [mm] | | | | | | | | |
| 18 | 5.5 | 2 | 6.75 | 3 | 13.25 | 11.2 | 4.3 | 15.2 |
| 25 | 5.5 | 2 | 9 | 4 | 15 | 13.35 | 7.65 | 22.35 |
| 32 | 6.6 | 2 | 10 | 5 | 19 | 9 | 9 | 29.5 |
| 40 | 6.6 | 2 | 10 | 6 | 20 | 12.6 | 12.2 | 32.8 |
| 63 | 11 | 3 | 13.5 | 8 | 28 | 17.5 | 12.5 | 55.5 |

| For Ø | B4 | B5 | H1 | H2 | H3 | H4 |
|-------|------|------|-------|-------|-------|-------|
| [mm] | | | | | | |
| 18 | 5.3 | 23.2 | 64 | 59.5 | 16 | 21.5 |
| 25 | 8.65 | 29.5 | 76.5 | 71.5 | 14.35 | 19.35 |
| 32 | 10.5 | 27 | 87.5 | 82.5 | 8 | 13 |
| 40 | 14.2 | 36.8 | 111.5 | 104.5 | 15.3 | 22.3 |
| 63 | 17.5 | 49 | 172.5 | 164.5 | 22 | 30 |

| For Ø | H6 | SA | TR | TR1 | US | Weight | Part No. | Type |
|-------|-----|-------|------|------|------|--------|----------|--------|
| [mm] | | -0.2 | ±0.1 | ±0.1 | | [g] | | |
| 18 | 7.7 | 176.5 | 30 | — | 38.6 | 58 | 533667 | HPC-18 |
| 25 | 8.5 | 230 | 40 | — | 55 | 131 | 533668 | HPC-25 |
| 32 | 9 | 288 | 56.5 | 19.5 | 68 | 239 | 533669 | HPC-32 |
| 40 | 12 | 340 | 65 | 25 | 78 | 348 | 533670 | HPC-40 |
| 63 | 19 | 456 | 111 | 39 | 133 | 1,245 | 545237 | HPC-63 |


Linear drives DGCI, with displacement encoder

FESTO

Accessories

Profile mounting MUC (order code: M)

Material:
High-alloy steel



The profile mounting can only be mounted underneath in combination with the clamping unit, shock absorber retainer DADP and intermediate position module DADM.

Area of application

→ 22

Dimensions and ordering data

| For Ø | AH | B1 | B2 | B3 | B4 | B5 | B6 | D1
Ø
H13 | D2
Ø
H7 |
|-------|------|-----------|-----------|------|------|------|-----|----------------|---------------|
| [mm] | | | ±0.2 | | | | | | |
| 18 | 27.2 | 67.8±0.2 | 56±0.15 | 28.7 | 27.2 | 23.2 | 5.7 | 5.5 | 5 |
| 25 | 32.5 | 79.5±0.2 | 65.5±0.15 | 28.5 | 37.5 | 29.5 | 7 | 5.5 | 5 |
| 32 | 37.5 | 94±0.2 | 80±0.15 | 35 | 47.5 | 37 | 7 | 5.5 | 5 |
| 40 | 47 | 110.5±0.2 | 96±0.15 | 43 | 57 | 46.8 | 7 | 6.5 | 6 |
| 63 | 75 | 169±0.5 | 149±0.2 | 72.5 | 87 | 69 | 10 | 9 | 6 |

| For Ø | H1 | H2 | H3 | H4 | L1 | L2 | L3 | Weight | Part No. | Type |
|-------|-------|---------------------|----------|------|--------|-------|------|--------|----------|--------|
| [mm] | | | | | | ±0.05 | ±0.2 | [g] | | |
| 18 | 64 | 5.7 _{-0.2} | 9.9±0.1 | 6.4 | 33±0.1 | 20.5 | – | 78 | 531752 | MUC-18 |
| 25 | 76.5 | 6.5 _{-0.2} | 12.5±0.1 | 7.43 | 35±0.1 | 22.5 | – | 113 | 531753 | MUC-25 |
| 32 | 87.5 | 6.5 _{-0.2} | 13±0.1 | 4 | 45±0.1 | 30 | – | 174 | 531754 | MUC-32 |
| 40 | 111.5 | 8.5 _{-0.2} | 16±0.1 | 11.3 | 60±0.1 | 44 | – | 346 | 531755 | MUC-40 |
| 63 | 172.5 | 11 | 25.5 | 15 | 80±0.4 | 26 | 56 | 1,080 | 531757 | MUC-63 |

Linear drives DGCI, with displacement encoder


FESTO

Accessories

Shock absorber retainer DADP-DGC Stop KYC

Materials: Stop
Housing: Anodised aluminium
Stop bracket: Stainless steel casting
Bracket: High-alloy steel
Free of copper and PTFE

Materials: Shock absorber retainer
Housing: Anodised aluminium
Free of copper and PTFE



 Note
Shock absorbers are not included in the scope of delivery.
Existing stop elements can be removed from the end caps of the linear drive and installed in the shock absorber retainer.

| Dimensions | | | | | | | | | |
|------------|------|------|----|---------|------|-----|------|-----|-------|
| For Ø | B1 | B2 | B3 | D1 | H1 | H2 | H3 | H4 | L1 |
| [mm] | | | | | | | | | |
| 18 | 16 | 34.5 | 29 | M12x1 | 20.7 | 0.2 | 12.5 | 0.7 | 128 |
| 25 | 16.5 | 35 | 30 | M16x1 | 25.5 | 0.5 | 15 | 1.4 | 168 |
| 32 | 16.5 | 35 | 30 | M16x1 | 25.5 | 0.5 | 15 | 1.7 | 206.8 |
| 40 | 16 | 35.7 | 35 | M22x1.5 | 37 | 0.5 | 21.5 | 2 | 255 |
| 63 | 25 | 50 | 40 | M26x1.5 | 51.5 | 1.5 | 33 | 0 | 328 |

| For Ø | L2 | L3 | L4 | L5 | L6 | L7 | | |
|-------|-------|-----|-----|-------|------|-------|-------|-----------|
| | | | | | | KF | KF-GP | KF-YSR(W) |
| [mm] | | | | | | | | |
| 18 | 74.5 | 107 | 80 | 118.5 | 23.5 | ≥14.5 | ≥18 | ≥14.5 |
| 25 | 100 | 136 | 80 | 125 | 20.5 | ≥22.5 | ≥25 | ≥22.5 |
| 32 | 124.8 | 164 | 120 | 165 | 14.5 | ≥27.3 | ≥27.3 | ≥27.3 |
| 40 | 150 | 210 | 156 | 220.5 | 31 | ≥31 | ≥37 | ≥31 |
| 63 | 200 | 256 | 200 | 268 | 24 | ≥41 | – | ≥41 |

 Note
For reasons of functional safety of the displacement encoder and stability of the linear drive DGCI, the distance L7 must not fall below the values in the table.


Linear drives DGCI, with displacement encoder

FESTO

Accessories

Technical data and ordering data


Precision adjustment



- - Note

The stop KYC can be used in both directions.

Installation example



- - Note

- The stop KYC can be mounted at any position along the stroke.
- Note dimension L7 → 40

| For Ø
[mm] | Max. impact force
[N] | Ambient temperature
[°C] | CRC ¹⁾ | Weight
[g] | Part No. | Type |
|----------------------------------|--------------------------|-----------------------------|-------------------|---------------|----------|----------------|
| Shock absorber retainer DADP-DGC | | | | | | |
| 18 | 1,100 | -10 ... +80 | 2 | 130 | 541729 | DADP-DGC-18-KF |
| 25 | 1,400 | | | 180 | 541730 | DADP-DGC-25-KF |
| 32 | 1,700 | | | 215 | 541731 | DADP-DGC-32-KF |
| 40 | 3,500 | | | 460 | 541732 | DADP-DGC-40-KF |
| 63 | 4,300 | | | 1,080 | 545245 | DADP-DGC-63 |

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

| For Ø
[mm] | Precision adjustment L
[mm] | Ambient temperature
[°C] | CRC ¹⁾ | Weight
[g] | Part No. | Type |
|---------------|--------------------------------|-----------------------------|-------------------|---------------|----------|--------|
| Stop KYC | | | | | | |
| 18 | 10 | -10 ... +80 | 2 | 400 | 541691 | KYC-18 |
| 25 | 10 | | | 560 | 541692 | KYC-25 |
| 32 | 10 | | | 790 | 541693 | KYC-32 |
| 40 | 15 | | | 1,525 | 541694 | KYC-40 |
| 63 | 15 | | | 2,950 | 545243 | KYC-63 |

- 1) Corrosion resistance class 2 according to Festo standard 940 070
Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.

- - Note

Permissible impact energy

→ 17

Linear drives DGCI, with displacement encoder

FESTO

Accessories

Intermediate position module DADM-DGC

Materials:


Housing: Anodised aluminium

Stop screw, nut: Galvanised steel

Bracket, lever:

High-alloy steel

Free of copper and PTFE



Note

- Shock absorbers are not included in the scope of delivery. Existing shock absorbers can be removed from the end caps of the linear drive and installed in the shock absorber retainer. Under no circumstances may the

linear drive and the intermediate position module be operated without a shock absorber.

- A shock absorber retainer DADP-DGC and a stop KYC are additionally needed when using an intermediate position module.

- The projection (dimension H4) must be observed when using the drive in combination with the intermediate position module DADM-DGC. Mounting via foot mountings HPC or profile mountings MUC is recommended in this case.

| Dimensions | | | | | | |
|------------|-------|------|----|----|------|------|
| For Ø [mm] | B1 | B2 | B3 | D1 | H1 | H2 |
| 25 | 122.5 | 16.5 | 40 | 19 | 69.4 | 68.6 |
| 32 | 138 | 16.5 | 40 | 19 | 80.2 | 79.7 |

| For Ø [mm] | H3 | H4 | L1 | L2 | L3 | L4 |
|------------|----|-----|-----|-----|------|------|
| 25 | 41 | 1.4 | 116 | 100 | 13.4 | 52.2 |
| 32 | 52 | 1.7 | 116 | 100 | 13.4 | 52.2 |

Note

Permissible impact energy

→ 17


Linear drives DGCI, with displacement encoder

FESTO

Accessories


Minimum distance

Between end stop and intermediate position



| Ø | L1 |
|----|-------|
| 25 | 145.3 |
| 32 | 185.3 |


Between two intermediate positions



| Ø | L2 | L3 | L4 |
|----|-----|-----|-----|
| 25 | 105 | 100 | 2.5 |
| 32 | 105 | 100 | 2.5 |

Technical data and ordering data


Precision adjustment L



- Note

The intermediate position module DADM-DGC can be used in both directions. A shock absorber retainer DADP-DGC and a stop KYC are additionally needed when using an intermediate position module.

Installation example



- Note

The intermediate position module DADM-DGC can be mounted at any position along the stroke.

| For Ø | Operating pressure | Impact velocity | Swivel time | Repetition accuracy | Pneumatic connection | Precision adjustment L |
|-------|--------------------|-----------------|-------------|---------------------|----------------------|------------------------|
| [mm] | [bar] | [m/s] | [ms] | [mm] | | [mm] |
| 25 | 2.5 ... 8 | → 21 | <100 | 0.02 | QS-4 | 2 |
| 32 | | | | | | |

| For Ø | Ambient temperature | CRC ¹⁾ | Mounting position | Position sensing | Weight | Part No. | Type |
|-------|---------------------|-------------------|-------------------|------------------------------------|--------|----------|---------------|
| [mm] | [°C] | | | | [g] | | |
| 25 | -10 ... +60 | 2 | Any | For proximity sensor
SME/SMT-10 | 430 | 541700 | DADM-DGC-25-A |
| 32 | | | | | 530 | 541701 | DADM-DGC-32-A |



1) Corrosion resistance class 2 according to Festo standard 940 070

Components subject to moderate corrosion stress. Externally visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment or media such as coolants or lubricating agents.


Linear drives DGCI, with displacement encoder

Accessories

FESTO

| Ordering data | | | | | | |
|---|-----------|--------------------------------|-------------------------------------|----------|------------------|------------------|
| | For Ø | Comment | Order code | Part No. | Type | PU ¹⁾ |
| Slot nut HMBN | | | Technical data → Internet: hmbn | | | |
|  | 25 ... 40 | For mounting slot | B | 547264 | HMBN-5-1M5 | 10 |
|  | 63 | | | 186566 | HMBN-5-2M5 | |
| | | | | | | |
| Centring pin/sleeve ZBS, ZBH | | | Technical data → Internet: zbs, zbh | | | |
|  | 18 | For slide | – | 150928 | ZBS-5 | 10 |
| | 25 ... 63 | | | 150927 | ZBH-9 | |
| | 18 | For end cap | – | 150928 | ZBS-5 | |
| | 25 ... 63 | | | 150927 | ZBH-9 | |
| | | | | | | |
| Slot cover ABP-S | | | Technical data → Internet: abp | | | |
|  | 18 ... 63 | For sensor slot
Every 0.5 m | L | 151680 | ABP-5-S | 2 |
| | | | | | | |
| Shock absorber YSRW | | | Technical data → Internet: ysrw | | | |
|  | 18 | | YSRW | 540347 | YSRW-DGC-18-KF | 1 |
| | 25 | | | 540349 | YSRW-DGC-25-KF | |
| | 32 | | | 540351 | YSRW-DGC-32-KF | |
| | 40 | | | 1232870 | YSRW-DGC-40/50-B | |
| | 63 | | | 543069 | YSRW-DGC-63 | |

1) Packaging unit


| Ordering data – Proportional directional control valves and push-in fittings | | | | | | |
|---|-------|---------------|--|--------------------------|---------------------------------------|--------------------------------------|
| | For Ø | Stroke | Proportional directional control valve | | Push-in fitting for DGCI | |
| | [mm] | [mm] | Technical data → Internet: vpwp | | Technical data → Internet: quick star | |
| | | | Part No. | Type | Part No. | PU ¹⁾ |
| For applications with axis controller CPX-CMAX | | | | | | |
|  | 18 | 100 ... 2,000 | 550170 | VPWP-4-L-5-Q6-10-E-... | 153306 | QSM-M5-6 |
| | 25 | 100 ... 160 | 550170 | VPWP-4-L-5-Q6-10-E-... | 186096 | QS-G ¹ / ₈ -6 |
| | | 225 ... 600 | 550170 | VPWP-4-L-5-Q8-10-E-... | 186098 | QS-G ¹ / ₈ -8 |
| | | 750 ... 2,000 | 550171 | VPWP-6-L-5-Q8-10-E-... | 186098 | QS-G ¹ / ₈ -8 |
| | 32 | 100 ... 400 | 550170 | VPWP-4-L-5-Q8-10-E-... | 186098 | QS-G ¹ / ₈ -8 |
| | | 450 ... 2,000 | 550171 | VPWP-4-L-5-Q8-10-E-... | 186098 | QS-G ¹ / ₈ -8 |
| | 40 | 100 ... 300 | 550170 | VPWP-4-L-5-Q8-10-E-... | 186099 | QS-G ¹ / ₄ -8 |
| | | 360 ... 750 | 550171 | VPWP-6-L-5-Q8-10-E-... | 186099 | QS-G ¹ / ₄ -8 |
| | | 850 ... 2,000 | 550172 | VPWP-8-L-5-Q10-10-E-... | 186101 | QS-G ¹ / ₄ -10 |
| | 63 | 100 ... 300 | 550171 | VPWP-6-L-5-Q8-10-E-... | 186100 | QS-G ³ / ₈ -8 |
| | | 360 ... 750 | 550172 | VPWP-8-L-5-Q10-10-E-... | 186102 | QS-G ³ / ₈ -10 |
| | | 850 ... 2,000 | 1552544 | VPWP-10-L-5-Q-10-E-G-EX1 | 186103 | QS-G ³ / ₈ -12 |

1) Packaging unit

Linear drives DGCI, with displacement encoder

FESTO

Accessories


| Ordering data – Proportional directional control valves and push-in fittings | | | | | | | |
|---|--|-----------------|--|--------------------------|---------------------------------------|--------------------------------------|------------------|
| | For Ø | Stroke | Proportional directional control valve | | Push-in fitting for DGCI | | |
| | [mm] | [mm] | Technical data → Internet: vpwp | | Technical data → Internet: quick star | | |
| | | | Part No. | Type | Part No. | Type | PU ¹⁾ |
|  | For applications with Soft Stop end-position controller CPX-CMPX, horizontal | | | | | | |
| | 18 | 100 ... 1,750 | 550170 | VPWP-4-L-5-Q6-10-E-... | 153306 | QSM-M5-6 | 10 |
| | | 2,000 | 550171 | VPWP-6-L-5-Q-10-E-... | 153306 | QSM-M5-6 | |
| | 25 | 100 ... 160 | 550170 | VPWP-4-L-5-Q6-10-E-... | 186096 | QS-G ¹ / ₈ -6 | |
| | | 225 ... 300 | 550170 | VPWP-4-L-5-Q8-10-E-... | 186098 | QS-G ¹ / ₈ -8 | |
| | | 360 ... 2,000 | 550171 | VPWP-6-L-5-Q8-10-E-... | 186098 | QS-G ¹ / ₈ -8 | |
| | 32 | 100 | 550170 | VPWP-4-L-5-Q6-10-E-... | 186096 | QS-G ¹ / ₈ -6 | |
| | | 160 ... 1,000 | 550171 | VPWP-6-L-5-Q8-10-E-... | 186098 | QS-G ¹ / ₈ -8 | |
| | | 1,250 ... 2,000 | 550172 | VPWP-8-L-5-Q-10-E-... | 186098 | QS-G ¹ / ₈ -8 | |
| | 40 | 100 ... 500 | 550171 | VPWP-6-L-5-Q8-10-E-... | 186099 | QS-G ¹ / ₄ -8 | |
| | | 600 ... 750 | 550172 | VPWP-8-L-5-Q-10-E-... | 186099 | QS-G ¹ / ₄ -8 | |
| | | 850 ... 2,000 | 550172 | VPWP-8-L-5-Q10-10-E-... | 186101 | QS-G ¹ / ₄ -10 | |
| | 63 | 100 ... 160 | 550170 | VPWP-4-L-5-Q8-10-E-... | 186100 | QS-G ³ / ₈ -8 | |
| | | 225 ... 300 | 550171 | VPWP-6-L-5-Q8-10-E-... | 186100 | QS-G ³ / ₈ -8 | |
| | | 360 ... 450 | 550172 | VPWP-8-L-5-Q10-10-E-... | 186102 | QS-G ³ / ₈ -10 | |
| | | 500 ... 2,000 | 1552544 | VPWP-10-L-5-Q-10-E-G-EX1 | 186103 | QS-G ³ / ₈ -12 | |
| | For applications with Soft Stop end-position controller CPX-CMPX, vertical | | | | | | |
| | 18 | 100 ... 1,750 | 550170 | VPWP-4-L-5-Q6-10-E-... | 153306 | QSM-M5-6 | 10 |
| | | 2,000 | 550171 | VPWP-6-L-5-Q-10-E-... | 153306 | QSM-M5-6 | |
| | 25 | 100 ... 160 | 550170 | VPWP-4-L-5-Q6-10-E-... | 186096 | QS-G ¹ / ₈ -6 | |
| 225 ... 750 | | 550170 | VPWP-4-L-5-Q8-10-E-... | 186098 | QS-G ¹ / ₈ -8 | | |
| 850 ... 2,000 | | 550171 | VPWP-6-L-5-Q8-10-E-... | 186098 | QS-G ¹ / ₈ -8 | | |
| 32 | 100 | 550170 | VPWP-4-L-5-Q6-10-E-... | 186096 | QS-G ¹ / ₈ -6 | | |
| | 160 ... 300 | 550170 | VPWP-4-L-5-Q8-10-E-... | 186098 | QS-G ¹ / ₈ -8 | | |
| | 360 ... 1,750 | 550171 | VPWP-6-L-5-Q8-10-E-... | 186098 | QS-G ¹ / ₈ -8 | | |
| | 2,000 | 550172 | VPWP-8-L-5-Q-10-E-... | 186098 | QS-G ¹ / ₈ -8 | | |
| 40 | 100 ... 225 | 550170 | VPWP-4-L-5-Q8-10-E-... | 186099 | QS-G ¹ / ₄ -8 | | |
| | 300 ... 750 | 550171 | VPWP-6-L-5-Q8-10-E-... | 186099 | QS-G ¹ / ₄ -8 | | |
| | 850 ... 1,000 | 550171 | VPWP-6-L-5-Q-10-E-... | 186101 | QS-G ¹ / ₄ -10 | | |
| | 1,250 ... 2,000 | 550172 | VPWP-8-L-5-Q10-10-E-... | 186101 | QS-G ¹ / ₄ -10 | | |
| 63 | 100 ... 160 | 550170 | VPWP-4-L-5-Q8-10-E-... | 186100 | QS-G ³ / ₈ -8 | | |
| | 225 ... 300 | 550171 | VPWP-6-L-5-Q8-10-E-... | 186100 | QS-G ³ / ₈ -8 | | |
| | 360 ... 450 | 550172 | VPWP-8-L-5-Q10-10-E-... | 186102 | QS-G ³ / ₈ -10 | | |
| | 500 ... 2,000 | 1552544 | VPWP-10-L-5-Q-10-E-G-EX1 | 186103 | QS-G ³ / ₈ -12 | | |

1) Packaging unit


Linear drives DGCI, with displacement encoder

Accessories

FESTO

| Ordering data – Proportional directional control valves and push-in fittings | | | | | | |
|---|--|---------------|--|---------------------|---------------------------------------|-----------------------|
| | For Ø | Stroke | Proportional directional control valve | | Push-in fitting for DGCI | |
| | [mm] | [mm] | Technical data → Internet: mpye | | Technical data → Internet: quick star | |
| | | | Part No. | Type | Part No. | Type PU ¹⁾ |
|  | For applications with axis controller SPC200 | | | | | |
| | 18 | 100 ... 300 | 154200 | MPYE-5-M5-010-B | 153306 | QSM-M5-6 10 |
| | | 360 ... 2,000 | 151692 | MPYE-5-1/8-LF-010-B | 153306 | QSM-M5-6 |
| | 25 | 100 ... 160 | 154200 | MPYE-5-M5-010-B | 186096 | QS-G1/8-6 |
| | | 225 ... 750 | 151692 | MPYE-5-1/8-LF-010-B | 186098 | QS-G1/8-8 |
| | | 850 ... 2,000 | 151693 | MPYE-5-1/8-HF-010-B | 186098 | QS-G1/8-8 |
| | 32 | 100 | 154200 | MPYE-5-M5-010-B | 186096 | QS-G1/8-6 |
| | | 160 ... 360 | 151692 | MPYE-5-1/8-LF-010-B | 186098 | QS-G1/8-8 |
| | | 450 ... 2,000 | 151693 | MPYE-5-1/8-HF-010-B | 186098 | QS-G1/8-8 |
| | 40 | 100 ... 300 | 151692 | MPYE-5-1/8-LF-010-B | 186099 | QS-G1/4-8 |
| | | 360 ... 750 | 151693 | MPYE-5-1/8-HF-010-B | 186099 | QS-G1/4-8 |
| | | 850 ... 2,000 | 151694 | MPYE-5-1/4-010-B | 186101 | QS-G1/4-10 |
| | 63 | 100 ... 160 | 151692 | MPYE-5-1/8-LF-010-B | 186100 | QS-G3/8-8 |
| | | 225 ... 300 | 151693 | MPYE-5-1/8-HF-010-B | 186100 | QS-G3/8-8 |
| | | 360 ... 450 | 151694 | MPYE-5-1/4-010-B | 186102 | QS-G3/8-10 |
| | | 500 ... 2,000 | 151695 | MPYE-5-3/8-010-B | 186103 | QS-G3/8-12 |

1) Packaging unit


| Ordering data – Proportional directional control valves and push-in fittings | | | | | | |
|---|---|-----------------|--|---------------------|---------------------------------------|-----------------------|
| | For Ø | Stroke | Proportional directional control valve | | Push-in fitting for DGCI | |
| | [mm] | [mm] | Technical data → Internet: mpye | | Technical data → Internet: quick star | |
| | | | Part No. | Type | Part No. | Type PU ¹⁾ |
|  | For applications with Soft Stop end-position controller SPC11-MTS-AIF-2, horizontal | | | | | |
| | 18 | 100 ... 300 | 154200 | MPYE-5-M5-010-B | 153306 | QSM-M5-6 10 |
| | | 360 ... 1,750 | 151692 | MPYE-5-1/8-LF-010-B | 153306 | QSM-M5-6 |
| | | 2,000 | 151693 | MPYE-5-1/8-HF-010-B | 153306 | QSM-M5-6 |
| | 25 | 100 ... 160 | 151692 | MPYE-5-1/8-LF-010-B | 186096 | QS-G1/8-6 |
| | | 225 ... 300 | 151692 | MPYE-5-1/8-LF-010-B | 186098 | QS-G1/8-8 |
| | | 360 ... 2,000 | 151693 | MPYE-5-1/8-HF-010-B | 186098 | QS-G1/8-8 |
| | 32 | 100 | 151692 | MPYE-5-1/8-LF-010-B | 186096 | QS-G1/8-6 |
| | | 160 ... 1,000 | 151693 | MPYE-5-1/8-HF-010-B | 186098 | QS-G1/8-8 |
| | | 1,250 ... 2,000 | 151694 | MPYE-5-1/4-010-B | 186098 | QS-G1/8-8 |
| | 40 | 100 ... 500 | 151693 | MPYE-5-1/8-HF-010-B | 186099 | QS-G1/4-8 |
| | | 600 ... 750 | 151694 | MPYE-5-1/4-010-B | 186099 | QS-G1/4-8 |
| | | 850 ... 2,000 | 151694 | MPYE-5-1/4-010-B | 186101 | QS-G1/4-10 |
| | 63 | 100 ... 160 | 151692 | MPYE-5-1/8-LF-010-B | 186100 | QS-G3/8-8 |
| | | 225 ... 300 | 151693 | MPYE-5-1/8-HF-010-B | 186100 | QS-G3/8-8 |
| | | 360 ... 450 | 151694 | MPYE-5-1/4-010-B | 186102 | QS-G3/8-10 |
| | | 500 ... 2,000 | 151695 | MPYE-5-3/8-010-B | 186103 | QS-G3/8-12 |

1) Packaging unit


Linear drives DGCI, with displacement encoder

FESTO

Accessories

| Ordering data – Proportional directional control valves and push-in fittings | | | | | | | |
|---|---|-----------------|--|---------------------|---------------------------------------|------------|------------------|
| | For Ø | Stroke | Proportional directional control valve | | Push-in fitting for DGCI | | |
| | [mm] | [mm] | Technical data → Internet: mpye | | Technical data → Internet: quick star | | |
| | | | Part No. | Type | Part No. | Type | PU ¹⁾ |
|  | For applications with Soft Stop end-position controller SPC11-MTS-AIF-2, vertical | | | | | | |
| | 18 | 100 ... 300 | 154200 | MPYE-5-M5-010-B | 153306 | QSM-M5-6 | 10 |
| | | 360 ... 1,750 | 151692 | MPYE-5-1/8-LF-010-B | 153306 | QSM-M5-6 | |
| | | 2,000 | 151693 | MPYE-5-1/8-HF-010-B | 153306 | QSM-M5-6 | |
| | 25 | 100 ... 160 | 151692 | MPYE-5-1/8-LF-010-B | 186096 | QS-G1/8-6 | |
| | | 225 ... 750 | 151692 | MPYE-5-1/8-LF-010-B | 186098 | QS-G1/8-8 | |
| | | 850 ... 2,000 | 151693 | MPYE-5-1/8-HF-010-B | 186098 | QS-G1/8-8 | |
| | 32 | 100 | 151692 | MPYE-5-1/8-LF-010-B | 186096 | QS-G1/8-6 | |
| | | 160 ... 300 | 151692 | MPYE-5-1/8-LF-010-B | 186098 | QS-G1/8-8 | |
| | | 360 ... 1,750 | 151693 | MPYE-5-1/8-HF-010-B | 186098 | QS-G1/8-8 | |
| | | 2,000 | 151694 | MPYE-5-1/4-010-B | 186098 | QS-G1/8-8 | |
| | 40 | 100 ... 225 | 151692 | MPYE-5-1/8-LF-010-B | 186099 | QS-G1/4-8 | |
| | | 300 ... 750 | 151693 | MPYE-5-1/8-HF-010-B | 186099 | QS-G1/4-8 | |
| | | 850 ... 1,000 | 151693 | MPYE-5-1/8-HF-010-B | 186101 | QS-G1/4-10 | |
| | | 1,250 ... 2,000 | 151694 | MPYE-5-1/4-010-B | 186101 | QS-G1/4-10 | |
| | 63 | 100 ... 160 | 151692 | MPYE-5-1/8-LF-010-B | 186100 | QS-G3/8-8 | |
| | | 225 ... 300 | 151693 | MPYE-5-1/8-HF-010-B | 186100 | QS-G3/8-8 | |
| | | 360 ... 450 | 151694 | MPYE-5-1/4-010-B | 186102 | QS-G3/8-10 | |
| | | 500 ... 2,000 | 151695 | MPYE-5-3/8-010-B | 186103 | QS-G3/8-12 | |

1) Packaging unit

| Ordering data – Connecting cables | | | | |
|--|-----------------------------------|---------------------|----------|---------------------|
| | Brief description | Cable length
[m] | Part No. | Type |
| Connection between axis controller CPX-CMAX/end-position controller CPX-CMPX and proportional directional control valve VPWP | | | | |
|  | Angled plug and angled socket | 0.25 | 540327 | KVI-CP-3-WS-WD-0,25 |
| | | 0.5 | 540328 | KVI-CP-3-WS-WD-0,5 |
| | | 2 | 540329 | KVI-CP-3-WS-WD-2 |
| | | 5 | 540330 | KVI-CP-3-WS-WD-5 |
| | | 8 | 540331 | KVI-CP-3-WS-WD-8 |
| | Straight plug and straight socket | 2 | 540332 | KVI-CP-3-GS-GD-2 |
| | | 5 | 540333 | KVI-CP-3-GS-GD-5 |
| | | 8 | 540334 | KVI-CP-3-GS-GD-8 |