


## Solenoid valves VUVG/valve terminals VTUG

FESTO



Festo Core Range  
Solves the majority of your automation tasks

Worldwide:  
Simply good:  
Fast:


Quickest delivery – wherever, whenever  
Expected high Festo quality  
Easy and fast to select

With the Festo Core Range, we have selected the most important products and functions from our broad product catalogue, and added the quickest delivery.

The Core Range offers you the best value for your automation tasks.

Just look  
for the  
star!

## Key features



### Innovative

- Can be set to internal or external pilot air supply for manifold assemblies with sub-base valves
- Maximum pressure 10 bar
- Design principle:
  - Piston spool with sealing ring (VUVG-LK, VUVG-BK)
  - Piston spool with sealing cartridge (VUVG-L, VUVG-B)

### Flexible

- Wide range of valve functions
- Choice of quick push-in connectors
- In-line valves
- Semi in-line valves for manifold assembly
- M5 and M7 in-line valves can be combined on one manifold rail
- Valve manifold assembly with pressure zones
- IP40, IP65
- Connection technology via:
  - E-box
  - Pneumatic interface CNOMO, to ISO 15218

### Reliable

- Sturdy and durable metal components
  - Valves
  - Manifold rails
- Fast troubleshooting thanks to 360° LED display
- Reliable servicing thanks to valves that can be replaced quickly and easily
- Choice of manual override: non-detenting, covered, non-detenting/de-tenting or detenting (without accessories)

### Easy to install

- Secure mounting on wall or H-rail
- Easy mounting, captive screws and seal
- Connection technology easy to change via the E-box
- Identification holder for labelling the valves

### Valve terminal configurator

A valve terminal configurator is available to help you select a suitable valve terminal VTUG. This makes it much easier to order the right product.

Valve terminals VTUG are ordered via an ident. code. All valve terminals are supplied fully assembled and individually tested.

Download CAD data → [www.festo.com](http://www.festo.com)


This reduces assembly and installation time to a minimum.

Ordering system for valve terminal VTUG  
→ Internet: vtug


## Key features – Pneumatic components

### Individual valves and valve manifold assemblies

In-line valves as individual valve




In-line valve VUVG-LK/VUVG-L




In-line valve VUVG-L to ISO 15218 (CNOMO)

### Semi in-line valves for manifold assembly




Semi in-line valve VUVG-S




Valve manifold assembly VTUG comprising semi in-line valves VUVG-S

### Sub-base valves for manifold assembly



Sub-base valve VUVG-BK/VUVG-B



Valve manifold assembly VTUG comprising sub-base valves VUVG-BK/VUVG-B

In-line valves are designed to be used without pneumatic links, as all connections to the fittings/tubing are on the valve. The electrical connection is provided by different E-boxes.

If a special seal set is used, in-line valves VUVG can also be mounted on a manifold rail (pneumatic linking) as semi in-line valves.

The in-line valve VTUG-L-...-P1 to ISO 15218 is a solenoid valve without electrical pilot control. The basic valve with the CNOMO pneumatic interface to ISO 15218 can be equipped with the following electrical pilot controls:

- Connection type C (DIN EN175301-803) or
- M12 connection (IEC 61076-2-101)

The supply ports (1, 3 and 5) for semi in-line valves are connected to the valve by common pneumatic links (e.g. sub-base).


The working ports (2, 4) are on the valve. The electrical connection is provided by different E-boxes.

The supply ports (1, 3 and 5) and the working ports (2, 4) of sub-base valves are connected through the sub-base or manifold to the valve.

The electrical connection is provided by different E-boxes.


## Key features – Pneumatic components

### Basic valves VUVG




- Size 10, 14 and 18 mm
- In-line valves and semi in-line valves
- Sub-base valves
- 2x 3/2-, 5/2- and 5/3-way valves

### E-boxes



- 5, 12 and 24 V DC
- With or without holding current reduction
- LED


### Combinations of basic valve and E-boxes



#### Note


More E-boxes → page 104

### Cover caps for manual override



- Closed cover cap, covered manual override
- Slotted cover cap, non-detenting manual override
- Cover, detenting manual override


### Identification holder



- The identification holder is mounted in the same way as a cover cap for manual override
- The hinged identification holder covers the retaining screw and the manual override


## Key features – Pneumatic components

### Manifold rail for in-line valves



- For in-line valves M3, M5, M7, G1/8 and G1/4
- For 2x 3/2-way, 5/2-way and 5/3-way valves
- 2 to 10 and 12, 14, 16 valve positions


### Manifold rail for sub-base valves



- For sub-base valves 10A, 10, 14 and 18
- Manifold rail with M5, M7, G1/8 and G1/4 working ports
- For 2x 3/2-way, 5/2-way and 5/3-way valves
- 2 to 10, 12, 14 and 16 valve positions
- The sub-base valves always have external pilot air. The pilot air is set via the manifold rail. A short and a long blanking plug are included in the scope of delivery of the manifold rail for this purpose.


 **Note**  
Pressurisation and exhaust at both ends is recommended for an optimised flow rate in cases where multiple valves switch simultaneously.

### Cover plate for vacant position



Vacant position cover

### Supply plate



For additional air supply and exhaust via a valve position

### Separator for pressure zones




For creating multiple pressure zones in a valve manifold assembly

## Key features – Pneumatic components

## Vertical pressure supply plate

For in-line valves M5/M7 and G1/8




- [1] In-line valves VUVG
- [2] Vertical pressure supply plate
- [3] Manifold rail

The vertical pressure supply plate allows for separate pressurisation and exhausting of the valve mounted on it. If two vertical pressure supply plates are mounted one on top of the other, the valve can be supplied with compressed air and exhausted completely independently of the valve terminal (terminal code CS).

Code		Type	For in-line valves		Description
			M5/M7	G1/8	
ZU		VABF-L1-P3A	■	■	Plate with port 1 for supplying an individual operating pressure or separate exhausting (reverse operation) for a valve position.
ZV		VABF-L1-P7A	■	■	Plate with ports 3 and 5 for exhausting the valve or supplying an individual operating pressure (reverse operation) for a valve position.

## Key features – Pneumatic components

### Exhaust functions



- [1] Valves VUVG with individual electrical connection
- [2] Flow restrictor for M5 thread
- [3] Fitting
- [4] Fixed flow restrictor, self-tapping/check valve

#### Flow restrictor for M5 thread

In-line valve, individual electrical connection: flow restrictor can be fitted in port 1, 3, 5 and/or in port 2, 4.

#### Fixed flow restrictor, self-tapping

The fixed flow restrictor can be used to permanently set the exhaust flow rate in ducts 3 and 5.

Sub-base valve, individual electrical connection: flow restrictor can be fitted in port 2, 4.

The fixed flow restrictors are screwed into ducts 3 and 5 in the manifold rail.  
Please see the relevant assembly instructions:  
→ [www.festo.com/sp](http://www.festo.com/sp)

#### Check valve

Check valves block the flow towards the valves if back pressure develops in ducts 3 and 5 in the case of a high exhaust capacity, thereby preventing actuators from switching unexpectedly. The check valves are screwed into ducts 3 and 5 in the manifold rail. Please see the relevant assembly instructions:

→ [www.festo.com/sp](http://www.festo.com/sp)

#### - Note

- It is not possible to use a check valve and a fixed flow restrictor (in the same duct) at the same time.
- When screwing in again, use the threads already present.

## Key features – Pneumatic components

### Creating pressure zones and separating exhaust air

Compressed air is supplied and exhausted via the manifold rail and via supply plates.

The position of the supply plates and channel separations can be freely selected with the VUVG.

Pressure zones are created by isolating the internal supply ducts between the manifold sub-bases by appropriate duct separation.









Pressure zone separation can be used for the following ducts:

- Duct 1
- Duct 3
- Duct 5


#### Note

- Use a separator if the exhaust air pressures are high
- Use at least one supply plate/air supply for each pressure zone
- Pressure zone separation is not possible in duct 12/14 (pilot air supply)

### Duct separation

	Description						
	<p>The pressure zones can be freely configured with the VUVG. The following duct separations are possible:</p> <table border="1"> <tr> <td>Duct 1 closed</td> <td></td> </tr> <tr> <td>Duct 1, 3, 5 closed</td> <td></td> </tr> <tr> <td>Duct 3, 5 closed</td> <td></td> </tr> </table>	Duct 1 closed		Duct 1, 3, 5 closed		Duct 3, 5 closed	
Duct 1 closed							
Duct 1, 3, 5 closed							
Duct 3, 5 closed							
	<p>The number of pressure zones with the VUVG is only limited by the number of valve positions on the manifold rail. Note that each supply plate occupies one valve position.</p>						

### Separator VABD



#### Note

As the separators are fitted from only one side using a slotted screwdriver, several pressure zones can be created in one profile.

## Key features – Pneumatic components

### Pilot air supply

#### Internal pilot air supply

Internal pilot air supply can be chosen with an operating pressure between 1.5 ... 8 bar, 2.5 ... 8 bar, or 3 ... 8 bar (depending on the valve used).

The pilot air supply is branched from duct 1 (compressed air supply) using an internal connection.


#### External pilot air supply

External pilot air supply is required for vacuum operation. The port for external pilot air supply (port 12/14) is located on the valve in the case of in-line valves and on the manifold rail in the case of sub-base valves.

#### Pilot exhaust air

With in-line valves, the pilot exhaust air escapes via exhaust holes. With sub-base valves, the pilot exhaust air is discharged via duct 82/84 of the manifold rail.

### Pilot air supply with in-line and semi in-line valves




- [1] Push-in fitting for external pilot air supply at port 12/14
- [2] Single solenoid valve with external pilot air supply
- [3] Single solenoid valve with internal pilot air supply
- [4] Double solenoid valve with external pilot air supply
- [5] Double solenoid valve with internal pilot air supply

The internal pilot air is branched from port 1 in the valve body. The external pilot air (port 12/14) is supplied individually at each valve housing.

#### Note

Semi in-line valves cannot be supplied centrally with pilot air via the manifold rail.

### Pilot air supply with sub-base valves



- [1] Blanking plug, short, with internal pilot air
- [2] Blanking plug for duct 12/14 with internal pilot air
- [3] Blanking plug, long, with external pilot air
- [4] Push-in fitting in duct 12/14 with external pilot air

The manifold rails for sub-base valves have an internal connection between duct 12/14 and duct 1. By inserting a blanking plug into this connection, it is possible to switch between internal and external pilot air.

## Key features – Pneumatic components

### Operation with different pressures

#### Vacuum operation

#### Points to note with 3/2-way valves

The 3/2-way valves are available in a design with two valves in one valve body and with pneumatic spring return. With these valves, the force for the return movement is obtained from port 1.

#### Note


Pressure must be present at port 1.

Vacuum operation is therefore only possible at port 3 and 5, not at port 1. With external pilot air supply, vacuum can be connected at port 1, 3, 5 of the 5/2-way and 5/3-way valves.

#### Reverse operation

The 3/2-way valves with pneumatic spring are not suitable for reverse operation, since at least the minimum pilot pressure must be present in duct 1.

#### Pressure deflector (internal pilot air)



- If two different pressures are required.
- Different pressures can be supplied at duct 1, 3 and 5.

#### Note


- With internal pilot air supply, the minimum pilot pressure must be adhered to in duct 1
- With 2x 3/2-way valves without spring return, the minimum pilot pressure must always be adhered to in duct 1

### Advantages

Any pressure or vacuum can be connected at ducts 3 and 5 both with external and internal pilot air.






#### Vacuum, ejector pulse and normal position

Vacuum, ejector pulse and normal position can be achieved as follows:





- Internal pilot air supply
- Vacuum in duct 3
- Pressure for the ejector pulse in duct 1

## Product range overview

Design	Working port	Size	Functions and flow rate [l/min]												→ Page/ Internet
			T32C	T32U	T32H	T32C/M	T32U/M	T32H/M	M52	M52/M	B52	P53C	P53U	P53E	
<b>In-line valve as individual valve, solenoid valve VUVG-LK</b>															
	M5	10	■ 180	—	—	—	—	—	■ 195	—	■ 195	—	—	—	27
	M7	10	■ 280	—	—	—	—	—	■ 340	—	■ 340	—	—	—	31
	G1/8	14	■ 570	—	—	—	—	—	■ 660	—	■ 660	—	—	—	48
<b>In-line valve as individual valve, solenoid valve VUVG-L</b>															
	M3	10A	—	—	—	—	—	—	■ 100	■ 80	■ 100	■ 90	■ 90	■ 90	21
	M5	10	■ 150	■ 150	■ 150	■ 135	■ 125	■ 125	■ 220	■ 190	■ 220	■ 210	■ 210	■ 210	35
	M7	10	■ 190	■ 190	■ 190	■ 150	■ 140	■ 140	■ 380	■ 320	■ 380	■ 320	■ 320	■ 320	40
	G1/8	14	■ 650	■ 600	■ 650	■ 550	■ 500	■ 500	■ 780	■ 780	■ 780	■ 650	■ 600	■ 600	52
	G1/4	18	■ 1000	■ 1000	■ 1000	■ 1000	■ 1000	■ 1000	■ 1300	■ 1300	■ 1380	■ 1200	■ 1000	■ 1000	62
<b>Semi in-line valve for manifold assembly, solenoid valve VUVG-S</b>															
	M3	10A	—	—	—	—	—	—	■ 100	■ 80	■ 100	■ 90	■ 90	■ 90	21
	M5	10	■ 150	■ 150	■ 150	■ 135	■ 125	■ 125	■ 220	■ 190	■ 220	■ 210	■ 210	■ 210	35
	M7	10	■ 170	■ 170	■ 170	■ 140	■ 130	■ 130	■ 340	■ 290	■ 340	■ 300	■ 300	■ 300	40
	G1/8	14	■ 620	■ 580	■ 580	■ 520	■ 480	■ 480	■ 730	■ 730	■ 730	■ 620	■ 580	■ 580	52
	G1/4	18	■ 1000	■ 1000	■ 1000	■ 1000	■ 1000	■ 1000	■ 1300	■ 1300	■ 1380	■ 1200	■ 1000	■ 1000	62
<b>Sub-base valve, solenoid valve VUVG-BK</b>															
	M5	10	■ 160	—	—	—	—	—	■ 160	—	■ 160	—	—	—	77
	M7	10	■ 160	—	—	—	—	—	■ 160	—	■ 160	—	—	—	77
	G1/8	14	■ 350	—	—	—	—	—	■ 380	—	■ 380	—	—	—	86
<b>Sub-base valve, solenoid valve VUVG-B</b>															
	M3	10A	—	—	—	—	—	—	■ 100	■ 80	■ 100	■ 90	■ 90	■ 90	72
	M5	10	■ 150	■ 150	■ 150	■ 130	■ 120	■ 120	■ 210	■ 180	■ 210	■ 200	■ 200	■ 200	80
	M7	10	■ 160	■ 160	■ 160	■ 140	■ 130	■ 130	■ 270	■ 230	■ 270	■ 250	■ 250	■ 250	80
	G1/8	14	■ 540	■ 510	■ 540	■ 430	■ 410	■ 410	■ 580	■ 580	■ 580	■ 540	■ 510	■ 510	86
	G1/4	18	■ 800	■ 800	■ 800	■ 800	■ 800	■ 800	■ 1000	■ 1000	■ 1000	■ 950	■ 950	■ 950	96

## Product range overview




Design	Size	Description	→ Page/ Internet
<b>Manifold rail VABM- ... -S- ... , for in-line valves (manifold assembly)</b>			
	10AS	Size M3	26, 46, 60, 70
	10S	Size M5, M7	
	14S	Size G1/8	
	18S	Size G1/4	
<b>Manifold rail VABM, for sub-base valves (manifold assembly)</b>			
	10AW	Size M3	76, 85, 95, 100
	10W	Size M5	
	10HW	Size M7	
	14W	Size G1/8	
	18W	Size G1/4	

## Overview of valve functions

Valve	Valve code	Description	VUVG-LK, VUVG-BK	VUVG-L, VUVG-B				
			Size M5/M7	Size G1/8	Size M3	Size M5/M7	Size G1/8	Size G1/4
<b>2x 3/2-way valve, normally closed, pneumatic spring</b>								
	T32C-A	In-line valve, pilot air supply Internal	■	■	-	■	■	■
		In-line valve, pilot air supply External	-	-	-	■	■	-
		Sub-base valve, external pilot air supply	-	-	-	■	■	■
<b>2x 3/2-way valve, normally open, pneumatic spring</b>								
	T32U-A	In-line valve, pilot air supply Internal	-	-	-	■	■	■
		In-line valve, pilot air supply External	-	-	-	■	■	-
		Sub-base valve, external pilot air supply	-	-	-	■	■	■
<b>2x 3/2-way valve, 1x normally open, 1x normally closed, pneumatic spring</b>								
	T32H-A	In-line valve, pilot air supply Internal	-	-	-	■	■	■
		In-line valve, pilot air supply External	-	-	-	■	■	-
		Sub-base valve, external pilot air supply	-	-	-	■	■	■

## Solenoid valves VUVG

### Overview of valve functions

Valve	Valve code	Description	VUVG-LK, VUVG-BK	VUVG-L, VUVG-B	Size	Size	
			M5/M7	G1/8			
<b>2x 3/2-way valve, normally closed, mechanical spring</b>							
 14 12 4 2 1 3 5	T32C-M	In-line valve, pilot air supply Internal	-	-	-	■	■
		In-line valve, pilot air supply External	-	-	-	■	■
		Sub-base valve, external pilot air supply	-	-	-	■	■
<b>2x 3/2-way valve, normally open, mechanical spring</b>							
 10(14) 10(12) 4 2 1 3 5	T32U-M	In-line valve, pilot air supply Internal	-	-	-	■	■
		In-line valve, pilot air supply External	-	-	-	■	■
		Sub-base valve, external pilot air supply	-	-	-	■	■
<b>2x 3/2-way valve, 1x normally open, 1x normally closed, mechanical spring</b>							
 14 10(12) 4 2 1 3 5	T32H-M	In-line valve, pilot air supply Internal	-	-	-	■	■
		In-line valve, pilot air supply External	-	-	-	■	■
		Sub-base valve, external pilot air supply	-	-	-	■	■

## Overview of valve functions

Valve	Valve code	Description	VUVG-LK, VUVG-BK	VUVG-L, VUVG-B			
		Size	Size				
		M5/M7	G1/8	M3	M5/M7	G1/8	G1/4
<b>5/2-way double solenoid valve</b>							
	B52	In-line valve, pilot air supply Internal	■	■	■	■	■
		In-line valve, pilot air supply External	-	-	■	■	■
		Sub-base valve, external pilot air supply	-	-	■	■	■
<b>5/2-way valve, single solenoid, pneumatic spring</b>							
	M52-A	In-line valve, pilot air supply Internal	■	■	-	-	■
		In-line valve, pilot air supply External	-	-	-	-	■
		Sub-base valve, external pilot air supply	-	-	-	-	■
<b>5/2-way single solenoid valve, mechanical spring</b>							
	M52-M	In-line valve, pilot air supply Internal	-	-	■	■	■
		In-line valve, pilot air supply External	-	-	■	■	■
		Sub-base valve, external pilot air supply	-	-	■	■	■
<b>5/2-way valve, single solenoid, pneumatic/mechanical spring</b>							
	M52-R	In-line valve, pilot air supply Internal	-	-	■	■	-
		In-line valve, pilot air supply External	-	-	■	■	-
		Sub-base valve, external pilot air supply	-	-	■	■	-


## Solenoid valves VUVG

### Overview of valve functions

Valve	Valve code	Description	VUVG-LK, VUVG-BK	VUVG-L, VUVG-B			
		Size	Size				
		M5/M7	G1/8	M3	M5/M7	G1/8	G1/4
<b>5/3-way valve, mid-position closed</b>							
	P53C	In-line valve, pilot air supply Internal	-	-	■	■	■
		In-line valve, pilot air supply External	-	-	■	■	■
		Sub-base valve, external pilot air supply	-	-	■	■	■
<b>5/3-way valve, mid-position pressurised</b>							
	P53U	In-line valve, pilot air supply Internal	-	-	■	■	■
		In-line valve, pilot air supply External	-	-	■	■	■
		Sub-base valve, external pilot air supply	-	-	■	■	■
<b>5/3-way valve, mid-position exhausted</b>							
	P53E	In-line valve, pilot air supply Internal	-	-	■	■	■
		In-line valve, pilot air supply External	-	-	■	■	■
		Sub-base valve, external pilot air supply	-	-	■	■	■

## Peripherals overview example – In-line valves

## Manifold assembly




## Manifold assembly and accessories

	Type	Description	→ Page/Internet
[1]	Manifold rail	VABM-L1...	For 2 to 10, 12, 14 and 16 valve positions
[2]	Solenoid valve	VUVG-LK...	In-line valve 2x 3/2-way, 5/2-way and 5/3-way
[3]	Solenoid valve	VUVG-L...	In-line valve 2x 3/2-way, 5/2-way and 5/3-way
[4]	Cover plate	VABB-L1...	For covering a vacant position
[5]	Supply plate	VABF-L1...	For air supply at duct 1 and duct 3 and 5
[6]	H-rail	NRH-35-2000	For mounting the valve manifold assembly
[7]	H-rail mounting	VAME-T-M4	2 pieces for fitting the valve manifold assembly on an H-rail
[8]	Separator	VABD...	For creating pressure zones
[9]	Plug socket with cable	NEBV-H1G2...-LE2	For E-box H2 and H3
[10]	Push-in fitting	QS...	Push-in fitting for duct 2 and 4
[11]	Push-in fitting	QS...	Push-in fitting for air supply at duct 1
[12]	Silencer	U...	For duct 3 and 5
[13]	Cover cap	VMPA-HB...-B	For manual override
[14]	Identification holder	ASLR-D	For labelling the valves, covering the retaining screw and the manual override
[15]	Cover	VAMC	For manual override

## Peripherals overview example – Sub-base valves

## Manifold assembly



## Manifold assembly and accessories

	Type	Description	→ Page/Internet
[1]	Manifold rail	VABM-L1-...	For 2 to 10, 12, 14 and 16 valve positions
[2]	Solenoid valve	VUVG-BK...	Sub-base valve 2x 3/2-way, 5/2-way and 5/3-way
[3]	Solenoid valve	VUVG-B...	Sub-base valve 2x 3/2-way, 5/2-way and 5/3-way
[4]	Cover plate	VABB-L1...	For covering a vacant position
[5]	Supply plate	VABF-L1...	For air supply at duct 1 and duct 3 and 5
[6]	H-rail	NRH-35-2000	For mounting the valve manifold assembly
[7]	H-rail mounting	VAME-T-M4	2 pieces for fitting the valve manifold assembly on an H-rail
[8]	Separator	VABD- ...	For creating pressure zones
[9]	Plug socket with cable	NEBV-H1G2-KN-...-LE2	For E-box H2 and H3
[10]	Push-in fitting	QS...	Push-in fitting for duct 2 and 4
[11]	Push-in fitting	QS...	Push-in fitting for air supply at duct 1
[12]	Silencer	U...	For duct 3 and 5
[13]	Push-in fitting	QS...	Push-in fitting for pilot air supply at duct 12/14
[14]	Silencer	U...	Silencer for pilot air exhaust at duct 82/84
[15]	Cover cap	VMPA-HB...-B	For manual override
[16]	Identification holder	ASLR-D	For labelling the valves, covering the retaining screw and the manual override
[17]	Cover	VAMC	For manual override

## Type codes

001	Series
VUVG	Solenoid valve
002	Directional control valve type
L	In-line valve
S	Semi-inline valve
B	Sub-base valve
003	Design principle
	Piston spool
K	Piston spool with sealing ring
004	Size
10A	Size 10, deviating flow
10	Size 10
14	Size 14
18	Size 18
005	Valve function
T32U	2x3/2-way valve, normally open
T32C	2x3/2-way valve, normally closed
T32H	2x3/2-way valve, 1x normally closed, 1x normally open
M52	5/2-way valve, single solenoid/monostable
B52	5/2-way valve, double solenoid/bistable
P53U	5/3-way valve, mid-position pressurised
P53E	5/3-way valve, mid-position exhausted
P53C	5/3-way valve, mid-position closed
006	Reset method for monostable/single solenoid valves
	None
A	Pneumatic spring
M	Mechanical spring
R	Mixed, pneumatic/mechanical spring
007	Pilot air
	Internal
Z	External
008	Manual override
	None
H	Non-detenting
S	Covered
Y	Detenting
T	Non-detenting, detenting with accessories

009	Pneumatic connection
F	Flange/sub-base
M3	M3
M5	M5
M7	M7
G18	G1/8
G14	G1/4
Q3	Push-in connector 3 mm
Q4	Push-in connector 4 mm
Q4H	Push-in connector 4 mm, with connecting thread M7
Q6	Push-in connector 6 mm
Q6H	Push-in connector 6 mm, with connecting thread M7
Q8	Push-in connector 8 mm
Q10	Push-in connector 10 mm
T18	Push-in connector 1/8"
T532	Push-in connector 5/32"
T316	Push-in connector 3/16"
T316H	Push-in connector for 3/16", M7
T14	Push-in connector 1/4"
T14H	Push-in connector for 1/4", M7
T38	Push-in connector 3/8"
T516	Push-in connector 5/16"
T516H	Push-in connector 5/16", M7
010	Exhaust
	No fitting
QN	With fitting
U	Silencer
011	Nominal operating voltage
	None
4	5 V DC
5	12 V DC
1	24 V DC
1A	24 V AC/50-60 Hz
012	Electrical connection
	None
P3	Without electrical sub-base
C1	Connection pattern type C, to EN 175 301
H2	Connection pattern H, horizontal plug
H3	Connection pattern H, vertical plug
S2	Connection pattern S, horizontal plug
S3	Connection pattern S, vertical connector
L1	Leads 0.5 m
L2	Leads 1 m
L3	Leads 2.5 m
L4	Leads 5 m
K6	Cable 0.5 m
K7	Cable 1 m
K8	Cable 2.5 m
K9	Cable 5 m
R8	Individual connector M8, 3-pin
R1	Individual connector M8, 4-pin
R3	Individual connector M12
P1	Interface for pilot valve (CNOMO small)
013	Circuitry
	None
R	Holding current reduction with integrated protective circuit

## Type codes

014	Display
	None
L	LED

015	Electrical valve accessories
	None
C1	Connecting cable, 0.5 m
C2	Connecting cable 1 m
C3	Connecting cable 2.5 m
C4	Connecting cable, 5 m
D	Connector socket type C
D3	Connecting cable 2.5 m, with plug socket type C
D4	Connecting cable 5 m, with plug socket type C
DL3	Connecting cable 2.5 m, with plug socket type C, LED
DL4	Connecting cable 5 m, with plug socket type C, LED
DL5	Connecting cable 10 m, with plug socket type C, LED
E3	Connecting cable 2.5 m, straight plug socket M12
E4	Connecting cable 5 m, straight plug socket M12
E6	Connecting cable 2.5 m, angled plug socket M12
E7	Connecting cable 5 m, angled plug socket M12
N1	Connecting cable 2.5 m, straight plug socket M8, 3-pin
N2	Connecting cable 5 m, straight plug socket M8, 3-pin
N3	Connecting cable 2.5 m, angled plug socket M8, 3-pin
N4	Connecting cable 5 m, angled plug socket M8, 3-pin
N5	Connecting cable 2.5 m, straight plug socket M8, 4-pin
N6	Connecting cable 5 m, straight plug socket M8, 4-pin
N7	Connecting cable 2.5 m, angled plug socket M8, 4-pin
N8	Connecting cable 5 m, angled plug socket M8, 4-pin
S1	Connecting cable, 0.5 m, S-connector
S2	Connecting cable 1 m, S-connector
S3	Connecting cable 2.5 m, S-connector
S4	Connecting cable, 5 m, S-plug
W1	Connecting cable, flying leads, 0.5 m
W2	Connecting cable, flying leads, 1 m
W3	Connecting cable, flying leads, 2.5 m
W4	Connecting cable, flying leads, 5 m
WS1	Connecting cable, S-plug with flying leads, 0.5 m
WS2	Connecting cable, S-plug with flying leads, 1 m
WS3	Connecting cable, S-plug with flying leads, 2.5 m
WS4	Connecting cable, S-plug with flying leads, 5 m

016	Version
	Expanded properties
S	Focused properties

## Data sheet

### Function

5/2-way, single solenoid  
5/2-way, double solenoid valve  
5/3C, 5/3U, 5/3E

Circuit symbols → page 13

- - Size 10 mm
- - Flow rate  
90 ... 100 l/min
- - Voltage  
5, 12 and 24 V DC



### General technical data VUVG-L

Valve function	M52-R	B52	M52-M	P53			
Normal position	–	–	–	C <sup>1)</sup>	U <sup>2)</sup>		E <sup>3)</sup>
Stable position	Monostable	Bistable	Monostable	Monostable			
Pneumatic spring reset	Yes <sup>4)</sup>	–	No	–			
Mechanical spring reset	Yes <sup>4)</sup>	–	Yes	Yes			
Vacuum operation at port 1	Only with external pilot air supply						
Design	Piston spool						
Sealing principle	Soft						
Type of actuation	Electrical						
Type of control	Piloted						
Pilot air supply	Internal or external						
Exhaust function	Can be throttled						
Manual override	Choice of non-detenting, covered, non-detenting/detenting or detenting						
Type of mounting	Optionally via through-holes <sup>5)</sup> or on manifold rail						
Mounting position	Any						
Nominal width	[mm]	2		1.4	2		
Standard nominal flow rate	[l/min]	100		80	90		
Flow rate on manifold rail	[l/min]	100		80	90		
Switching time on/off	[ms]	7/15	–	7/21	8/25		
Switching time changeover	[ms]	–	5	–	14		
Size	[mm]	10					
Connection	1, 2, 3, 4, 5, 12/14	M3					
Product weight	[g]	38	49	37			
Certification	c UL us - Recognized (OL) RCM compliance mark						
CE marking (see declaration of conformity) <sup>6)</sup>	To EU EMC Directive						
Corrosion resistance class CRC <sup>7)</sup>	2						

1) C=Normally closed/mid-position closed

2) U=Normally open/mid-position pressurised

3) E=Mid-position exhausted

4) Combined reset method

5) If several valves are to be screwed together via the through-holes to form a block, a minimum distance of 0.3 mm must be ensured by placing spacer discs between them.

6) For information about the area of use, see the EC declaration of conformity at: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/) → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

7) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

## Data sheet

Operating and environmental conditions		M52-R <sup>1)</sup>	B52	M52-M <sup>2)</sup>	P53
Valve function		Compressed air to ISO 8573-2010 [7:4:4]			
Operating medium	Internal	[MPa]	0.25 ... 0.8	0.15 ... 0.8	0.3 ... 0.8
		[bar]	2.5 ... 8	1.5 ... 8	3 ... 8
	External	[MPa]	–0.09 ... 1		
		[bar]	–0.9 ... 10		
Pilot pressure	[MPa]	0.25 ... 0.8	0.15 ... 0.8	0.3 ... 0.8	
	[bar]	2.5 ... 8	1.5 ... 8	3 ... 8	
Ambient temperature	[°C]	–5 ... +50, with holding current reduction –5 ... +60			
Temperature of medium	[°C]	–5 ... +50, with holding current reduction –5 ... +60			

1) Mixed, pneumatic/mechanical spring

2) Mechanical spring

## Electrical data

Electrical connection	Via E-box → page 102
Operating voltage	[V DC] 5, 12 and 24 ±10%
Power	[W] 1, reduced to 0.35 with holding current reduction
Duty cycle	[%) 100
Degree of protection to EN 60529	IP40 (with plug socket), IP65 (with M8)




## Information on materials

Housing	Wrought aluminium alloy
Seals	HNBR, NBR
Note on materials	RoHS-compliant

## Data sheet

## Dimensions

5/2-way and 5/3-way valve

Download CAD data → [www.festo.com](http://www.festo.com)

**Note**

Additional dimensions

E-boxes

→ Page 104

[1] Electrical connection for solenoid valve, horizontal

[2] Manual override


[3] Port for external pilot air supply

Type	B1	B2	B3	D1	D2	D3	H1	H2	L1	L2	L3	L4	L5
VUVG-L10A-....M3...	10.2	3.6	2.83	M3	3.2	M3	32.5	4.4	74.3	69.3	8	18.5	25.4
VUVG-S10A-....M3...													

Type	L6	L7	L8	L9	L10	L11	L12	L13	L14	L15	L16	L17
VUVG-L10A-....M3...	4.85	6.15	34.9	7	11.9	7.3	15.25	28.5	6.7	8.54	57.06	54.56
VUVG-S10A-....M3...												

## Ordering data

Ordering data	Description	Part no.	Type	
<b>In-line valve M3, without E-box</b>				
	<b>5/2-way single solenoid valve</b>			
	Internal pilot air supply	Pneumatic/mechanical spring reset	566437	VUVG-L10A-M52-RT-M3-1P3
		Mechanical spring reset	574345	VUVG-L10A-M52-MT-M3-1P3
	External pilot air supply	Pneumatic/mechanical spring reset	566443	VUVG-L10A-M52-RZT-M3-1P3
		Mechanical spring reset	574346	VUVG-L10A-M52-MZT-M3-1P3
	<b>5/2-way double solenoid valve</b>			
	Internal pilot air supply		566438	VUVG-L10A-B52-T-M3-1P3
	External pilot air supply		566444	VUVG-L10A-B52-ZT-M3-1P3
<b>5/3-way valve</b>				
Internal pilot air supply	Mid-position closed, mechanical spring reset	566439	VUVG-L10A-P53C-T-M3-1P3	
	Mid-position exhausted, mechanical spring reset	566440	VUVG-L10A-P53E-T-M3-1P3	
	Mid-position pressurised, mechanical spring reset	566441	VUVG-L10A-P53U-T-M3-1P3	
External pilot air supply	Mid-position closed, mechanical spring reset	566445	VUVG-L10A-P53C-ZT-M3-1P3	
	Mid-position exhausted, mechanical spring reset	566446	VUVG-L10A-P53E-ZT-M3-1P3	
	Mid-position pressurised, mechanical spring reset	566447	VUVG-L10A-P53U-ZT-M3-1P3	


## Manifold assembly

### In-line valves for manifold assembly



#### Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



Note

Additional dimensions

E-boxes

→ Page 104

[1] Ports 1, 3 and 5: M5 (at both ends)

[2] Ports 2 and 4: M3

[5] Electrical connection for E-boxes and accessories

[6] H-rail mounting (two M4x16 screws are required for mounting)  
[7] Cover plate

[8] Supply plate, ports 1, 3 and 5: M5

[9] Valves/cover plate mounting on manifold rail: M2 thread

Type	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	D1
VABM-L1-10AS-M5	85.3	62.6	29.7	18.7	7.7	3	40.3	6.8	24.2	46.7	38.6	M5

Type	D2	H1	H2	H3	H4	H5	H6	L3	L5	L6	L7	L8	L9
VABM-L1-10AS-M5	Ø 4.5	43.8	10	5.5	16.2	6.8	20.3	7	12.5	10.3	10.5	3.5	14

Valve positions	2	3	4	5	6	7	8	9	10	12	14	16
L1	42.5	53	63.5	74	84.5	95	105.5	116	126.5	147.5	168.5	189.5
L2	28.5	39	49.5	60	70.5	81	91.5	102	112.5	133.5	154.5	175.5
L4	35.5	46	56.5	67	77.5	88	98.5	109	119.5	140.5	161.5	182.5
VABM weight [g]	26	34	42	50	58	66	74	82	90	106	122	138




## Ordering data

Technical data – Manifold rails			Operating pressure		Max. tightening torque for assembly [Nm]		
Connection	CRC	Material <sup>2)</sup>	[MPa]	[bar]	Valve	H-rail	Wall
1, 3, 5	M5	2 <sup>1)</sup> Wrought aluminium alloy	-0.09 ... 1	-0.9 ... 10	0.45	1.5	3

1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.


2) Note on materials: RoHS-compliant.

Ordering data – Manifold rail		Description	Part no.	Type
<b>Manifold rail for in-line valves (manifold assembly)</b>				
	For size M3	2 valve positions 3 valve positions 4 valve positions 5 valve positions 6 valve positions 7 valve positions 8 valve positions 9 valve positions 10 valve positions 12 valve positions 14 valve positions 16 valve positions	566522 566523 566524 566525 566526 566527 566528 566529 566530 566531 566532 566533	VABM-L1-10AS-M5-2 VABM-L1-10AS-M5-3 VABM-L1-10AS-M5-4 VABM-L1-10AS-M5-5 VABM-L1-10AS-M5-6 VABM-L1-10AS-M5-7 VABM-L1-10AS-M5-8 VABM-L1-10AS-M5-9 VABM-L1-10AS-M5-10 VABM-L1-10AS-M5-12 VABM-L1-10AS-M5-14 VABM-L1-10AS-M5-16
<b>Cover plate</b> Data sheets → Internet: vabb				
	For valve position on manifold rail, including screws and seal		569986	VABB-L1-10A
<b>Separator</b> Data sheets → Internet: vabd				
	For creating pressure zones		570872	VABD-4.2-B
<b>Supply plate</b> Data sheets → Internet: vabf				
	For valve position on manifold rail, including screws and seal		569990	VABF-L1-10A-P3A4-M5
<b>Seals for in-line valves</b> Data sheets → Internet: vabd				
	For in-line valves M3	Delivery quantity: 10 sets (each with 2 screws and 1 seal)	566670	VABD-L1-10AX-S-M3

## Data sheet

Function  
2x 3/2C  
5/2-way, single solenoid  
5/2-way, double solenoid valve  
  
Circuit symbols → page 13

- - Size 10 mm
- - Flow rate  
180 ... 195 l/min
- - Voltage  
24 V DC



### General technical data VUVG-LK

Valve function	T32-A	M52-A	B52
Normal position	C <sup>1)</sup>	-	-
Stable position	Monostable		Bistable
Pneumatic spring reset	Yes	Yes	-
Design	Piston spool		
Sealing principle	Soft		
Type of actuation	Electrical		
Type of control	Piloted		
Pilot air supply	Internal		
Exhaust function	Can be throttled		
Manual override	Detenting, non-detenting		
Type of mounting	Optionally via through-holes <sup>2)</sup> or on manifold rail		
Mounting position	Any		
Standard nominal flow rate	[l/min]	180	195
Switching time on/off	[ms]	12/14	14/17
Switching time changeover	[ms]	-	7
Size	[mm]	10	
Connection	2, 4	M5	
Product weight	[g]	55	45
Corrosion resistance class CRC <sup>3)</sup>		2	57

1) C=Normally closed

2) If several valves are to be screwed together via the through-holes to form a block, a minimum distance of 0.3 mm must be ensured by placing spacer discs between them.

3) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

### Safety data

Max. positive test pulse with 0 signal	[μs]	1600
Max. negative test pulse with 1 signal	[μs]	3000
Shock resistance		Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27
Vibration resistance		Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6

## Data sheet

Operating and environmental conditions			
Valve function	T32-A <sup>1)</sup>	M52-A <sup>1)</sup>	B52
Operating medium	Compressed air to ISO 8573-2010 [7:4:4]		
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)		
Operating pressure	[MPa]	0.15 ... 0.7	0.25 ... 0.7
	[bar]	1.5 ... 7	2.5 ... 7
Ambient temperature	[°C]	-5 ... +50	1.5 ... 7
Temperature of medium	[°C]	-5 ... +50	


1) Pneumatic spring

Electrical data	
Electrical connection	Via E-box → page 104
Operating voltage	[V DC] 24 ±10%
Power	[W] 0.7
Duty cycle	[%) 100
Degree of protection to EN 60529	IP40 (with plug socket), IP65 (with M8)
Signal status display	LED
Maximum switching frequency	[Hz] 2

Information on materials	
Housing	Wrought aluminium alloy
Seals	HNBR, NBR
Note on materials	RoHS-compliant Contains paint-wetting impairment substances

Pin allocation for E-box			
	Pin		Description
<b>Rectangular plug, connection pattern H</b>			
2	1	+ or -	Protective circuit without holding current reduction
	2	+ or -	
<b>Round plug, M8, 3-pin</b>			
4	1	Not used	Protective circuit without holding current reduction
+	3	+ or -	
+	4	+ or -	

## Protective circuit without holding current reduction



The solenoid coils have a protective circuit to arrest sparks and protect against polarity reversal.



## Data sheet

## Dimensions

2x 3/2-way, 5/2-way valve, double solenoid

Download CAD data → [www.festo.com](http://www.festo.com)

5/2-way single solenoid valve



- - Note

Additional dimensions

E-boxes

→ Page 104

[2] Horizontal electrical connection



[3] Manual override

Type	B1	D1	D2	H1	H3	L1	L2	L3	L4
VUVG-LK10-T32C-...-M5...	10.2	M5	3.3	33.6	7.8	98.3	95.8	35.7	27
VUVG-LK10-B52-...-M5...									
VUVG-LK10-M52-...-M5...						75.9	74.6		

Type	L5	L7	L8	L9	L10	L11
VUVG-LK10-T32C-...-M5...	34.4					
VUVG-LK10-B52-...-M5...		47				
VUVG-LK10-M52-...-M5...	13.2					

## Ordering data


### ★ Core product range

Ordering data	Description	Part no.	Type
<b>In-line valve M5, with E-box R8</b>			
	<b>2x 3/2-way valve</b> Internal pilot air supply      Normally closed, pneumatic spring reset	★ 8042542	VUVG-LK10-T32C-AT-M5-1R8L-S
	<b>5/2-way single solenoid valve</b> Internal pilot air supply      Pneumatic spring reset	★ 8042543	VUVG-LK10-M52-AT-M5-1R8L-S
	<b>5/2-way double solenoid valve</b> Internal pilot air supply	★ 8042544	VUVG-LK10-B52-T-M5-1R8L-S
<b>In-line valve M5, with E-box H2</b>			
	<b>2x 3/2-way valve</b> Internal pilot air supply      Normally closed, pneumatic spring reset	★ 8042538	VUVG-LK10-T32C-AT-M5-1H2L-S
	<b>5/2-way single solenoid valve</b> Internal pilot air supply      Pneumatic spring reset	★ 8042539	VUVG-LK10-M52-AT-M5-1H2L-S
	<b>5/2-way double solenoid valve</b> Internal pilot air supply	★ 8042540	VUVG-LK10-B52-T-M5-1H2L-S

## Data sheet

Function  
2x 3/2C  
5/2-way, single solenoid  
5/2-way, double solenoid valve  
  
Circuit symbols → page 13

- - Size 10 mm
- - Flow rate  
280 ... 340 l/min
- - Voltage  
24 V DC



### General technical data VUVG-LK

Valve function	T32-A	M52-A	B52
Normal position	C <sup>1)</sup>	-	-
Stable position	Monostable		Bistable
Pneumatic spring reset	Yes	Yes	-
Design	Piston spool		
Sealing principle	Soft		
Type of actuation	Electrical		
Type of control	Piloted		
Pilot air supply	Internal		
Exhaust function	Can be throttled		
Manual override	Detenting, non-detenting		
Type of mounting	Optionally via through-holes <sup>2)</sup> or on manifold rail		
Mounting position	Any		
Standard nominal flow rate	[l/min]	280	340
Switching time on/off	[ms]	12/14	14/17
Switching time changeover	[ms]	-	7
Size	[mm]	10	
Connection	2, 4	M7	
Product weight	[g]	55	45
Corrosion resistance class CRC <sup>3)</sup>		2	57

1) C=Normally closed

2) If several valves are to be screwed together via the through-holes to form a block, a minimum distance of 0.3 mm must be ensured by placing spacer discs between them.

3) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

### Safety data

Max. positive test pulse with 0 signal	[μs]	1600
Max. negative test pulse with 1 signal	[μs]	3000
Shock resistance		Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27
Vibration resistance		Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6

## Data sheet

Operating and environmental conditions			
Valve function	T32-A <sup>1)</sup>	M52-A <sup>1)</sup>	B52
Operating medium	Compressed air to ISO 8573-2010 [7:4:4]		
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)		
Operating pressure	[MPa]	0.15 ... 0.7	0.25 ... 0.7
	[bar]	1.5 ... 7	2.5 ... 7
Ambient temperature	[°C]	-5 ... +50	1.5 ... 7
Temperature of medium	[°C]	-5 ... +50	


1) Pneumatic spring

Electrical data	
Electrical connection	Via E-box → page 102
Operating voltage	[V DC] 24 ±10%
Power	[W] 0.7
Duty cycle	[%) 100
Degree of protection to EN 60529	IP40 (with plug socket), IP65 (with M8)
Signal status display	LED
Maximum switching frequency	[Hz] 2

Information on materials	
Housing	Wrought aluminium alloy
Seals	HNBR, NBR
Note on materials	RoHS-compliant Contains paint-wetting impairment substances

Pin allocation for E-box	Pin	Description
<b>Rectangular plug, connection pattern H</b>		
	1	+ or -
	2	+ or -
<b>Round plug, M8, 3-pin</b>		
	1	Not used
	3	+ or -
	4	+ or -

## Protective circuit without holding current reduction




The solenoid coils have a protective circuit to arrest sparks and protect against polarity reversal.

## Data sheet

## Dimensions

2x 3/2-way, 5/2-way valve, double solenoid




[2] Horizontal electrical connection

[3] Manual override

Download CAD data → [www.festo.com](http://www.festo.com)

5/2-way single solenoid valve



- - - Note
- Additional dimensions
- E-boxes
- Page 104



Type	B1	D1	D2	H1	H3	L1	L2	L3	L4
VUVG-LK10-T32C-...-M7...	10.2	M7	3.3	33.6	7.8	98.3	95.8	35.7	27
VUVG-LK10-B52-...-M7...						75.9	74.6	35.7	
VUVG-LK10-M52-...-M7...									

Type	L5	L7	L8	L9	L10	L11
VUVG-LK10-T32C-...-M7...	34.4		47	12.5	11	11.7
VUVG-LK10-B52-...-M7...						17.7
VUVG-LK10-M52-...-M7...	13.2					

## Ordering data

## ★ Core product range

Ordering data	Description	Part no.	Type
<b>In-line valve M7, with E-box R8</b>			
	<b>2x 3/2-way valve</b> Internal pilot air supply      Normally closed, pneumatic spring reset	★ 8042550	VUVG-LK10-T32C-AT-M7-1R8L-S
	<b>5/2-way single solenoid valve</b> Internal pilot air supply      Pneumatic spring reset	★ 8042551	VUVG-LK10-M52-AT-M7-1R8L-S
	<b>5/2-way double solenoid valve</b> Internal pilot air supply	★ 8042552	VUVG-LK10-B52-T-M7-1R8L-S
<b>In-line valve M7, with E-box H2</b>			
	<b>2x 3/2-way valve</b> Internal pilot air supply      Normally closed, pneumatic spring reset	★ 8042546	VUVG-LK10-T32C-AT-M7-1H2L-S
	<b>5/2-way single solenoid valve</b> Internal pilot air supply      Pneumatic spring reset	★ 8042547	VUVG-LK10-M52-AT-M7-1H2L-S
	<b>5/2-way double solenoid valve</b> Internal pilot air supply	★ 8042548	VUVG-LK10-B52-T-M7-1H2L-S

## Data sheet

### Function

2x 3/2C, 2x 3/2U, 2x 3/2H

5/2-way, single solenoid

5/2-way, double solenoid valve

5/3C, 5/3U, 5/3E

Circuit symbols → page 13

- - Size 10 mm

- - Flow rate  
125 ... 220 l/min

- - Voltage  
5, 12 and 24 V DC



### General technical data VUVG-L M5

Valve function	T32-A	T32-M			M52-R	B52	M52-M	P53										
	C <sup>1)</sup>	U <sup>2)</sup>	H <sup>4)</sup>	C <sup>1)</sup>	U <sup>2)</sup>	H <sup>4)</sup>												
Normal position								C <sup>1)</sup> U <sup>2)</sup> E <sup>3)</sup>										
Stable position	Monostable						Bistable	Monostable										
Pneumatic spring reset	Yes	No			Yes <sup>5)</sup>													
Mechanical spring reset	No	Yes			Yes <sup>5)</sup>													
Vacuum operation at port 1	No	Only with external pilot air supply																
Design	Piston spool																	
Sealing principle	Soft																	
Type of actuation	Electrical																	
Type of control	Piloted																	
Pilot air supply	Internal or external																	
Exhaust function	Can be throttled																	
Manual override	Choice of non-detenting, covered, non-detenting/detenting or detenting																	
Type of mounting	Optionally via through-holes <sup>6)</sup> or on manifold rail																	
Mounting position	Any																	
Nominal width	[mm]	2.7	1.9	1.8	3.2	2.2	3.2											
Standard nominal flow rate	[l/min]	150	135	125	125	220	190	210										
Flow rate on manifold rail	[l/min]	150	135	125	125	220	190	210										
Switching time on/off	[ms]	6/15	8/11			7/17	-	8/24										
Switching time changeover	[ms]	-				7	-	14										
Size	[mm]	10																
Connection	1, 2, 3, 4, 5 12/14	M5 M3																
Product weight	[g]	55	54			45	55	44										
Certification	c UL us - Recognized (OL) RCM compliance mark																	
CE marking (see declaration of conformity) <sup>7)</sup>	To EU EMC Directive																	
Corrosion resistance class CRC <sup>8)</sup>	2																	

1) C=Normally closed/mid-position closed

2) U=Normally open/mid-position pressurised

3) E=Mid-position exhausted

4) H=2x 3/2-way valve in one housing with 1x normally closed and 1x normally open

5) Combined reset method

6) If several valves are to be screwed together via the through-holes to form a block, a minimum distance of 0.3 mm must be ensured by placing spacer discs between them.

7) For information about the area of use, see the EC declaration of conformity at: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/) → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

8) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

## Data sheet

Operating and environmental conditions		T32-A <sup>1)</sup>	T32-M <sup>3)</sup>	M52-R <sup>2)</sup>	B52	M52-M <sup>3)</sup>	P53
Valve function							
Operating medium	Compressed air to ISO 8573-2010 [7:4:4]						
Operating pressure	Internal	[MPa]	0.15 ... 0.8	0.25 ... 0.8	0.25 ... 0.8	0.15 ... 0.8	0.3 ... 0.8
		[bar]	1.5 ... 8	2.5 ... 8	2.5 ... 8	1.5 ... 8	3 ... 8
	External	[MPa]	0.15 ... 1	-0.09 ... 1		-0.09 ... 0.8	-0.09 ... 1
		[bar]	1.5 ... 10	-0.9 ... 10		-0.9 ... 8	-0.9 ... 10
Pilot pressure	[MPa]	0.15 ... 0.8	0.2 ... 0.8	0.25 ... 0.8	0.15 ... 0.8	0.3 ... 0.8	
	[bar]	1.5 ... 8	2 ... 8	2.5 ... 8	1.5 ... 8	3 ... 8	
Ambient temperature	[°C]	-5 ... +50, with holding current reduction -5 ... +60					
Temperature of medium	[°C]	-5 ... +50, with holding current reduction -5 ... +60					

1) Pneumatic spring

2) Mixed, pneumatic/mechanical spring

3) Mechanical spring



Electrical data	
Electrical connection	Via E-box → page 102
Operating voltage	[V DC] 5, 12 and 24 ±10%
Power	[W] 1, reduced to 0.35 with holding current reduction
Duty cycle	[%) 100
Degree of protection to EN 60529	IP40 (with plug socket), IP65 (with M8)

Information on materials	
Housing	Wrought aluminium alloy
Seals	HNBR, NBR
Note on materials	RoHS-compliant

## Data sheet

## Dimensions

2x 3/2-way, 5/2-way and 5/3-way valve

Download CAD data → [www.festo.com](http://www.festo.com)

- - Note  
Additional dimensions  
E-boxes  
→ Page 104

[1] Vertical electrical connection

[2] Horizontal electrical connection

[3] Manual override



[4] Port for external pilot air supply

Type	B1	B2	D1	D2	D3	H1	H2	H3	L1	L2	L3	L4
VUVG-L-10 ....M5...	10.2	-	M5	3.2	M3	32.5	3.6	4.4	86.5	81.5	8	27
VUVG-S-10 ....M5...												





Type	L5	L6	L7	L8	L9	L10	L11	L12	L13	L14
VUVG-L-10 ....M5...	4.85	6.15	47	14	11	12	19	-	69.2	66.7
VUVG-S-10 ....M5...										

## Ordering data

### ★ Core product range

Ordering data	Description	Part no.	Type
<b>In-line valve M5, with E-box R8</b>			
	<b>5/3-way valve</b> Internal pilot air supply Mid-position closed, mechanical spring reset	★ 577346	VUVG-L10-P53C-T-M5-1R8L
<b>In-line valve M5, without E-box</b>			
	<b>2x 3/2-way valve</b> Internal pilot air supply Normally closed, pneumatic spring reset Normally open, pneumatic spring reset 1x normally open, 1x normally closed, pneumatic spring reset Normally closed, mechanical spring reset Normally open, mechanical spring reset 1x normally open, 1x normally closed, mechanical spring reset	566454	VUVG-L10-T32C-AT-M5-1P3
	566455	VUVG-L10-T32U-AT-M5-1P3	
	566456	VUVG-L10-T32H-AT-M5-1P3	
	574348	VUVG-L10-T32C-MT-M5-1P3	
	574349	VUVG-L10-T32U-MT-M5-1P3	
	574350	VUVG-L10-T32H-MT-M5-1P3	
	566463	VUVG-L10-T32C-AZT-M5-1P3	
	External pilot air supply Normally closed, pneumatic spring reset Normally open, pneumatic spring reset 1x normally open, 1x normally closed, pneumatic spring reset Normally closed, mechanical spring reset Normally open, mechanical spring reset 1x normally open, 1x normally closed, mechanical spring reset	566464	VUVG-L10-T32U-AZT-M5-1P3
		566465	VUVG-L10-T32H-AZT-M5-1P3
		574352	VUVG-L10-T32C-MZT-M5-1P3
		574353	VUVG-L10-T32U-MZT-M5-1P3
		574354	VUVG-L10-T32H-MZT-M5-1P3
		566457	VUVG-L10-M52-RT-M5-1P3
	Internal pilot air supply Pneumatic/mechanical spring reset Mechanical spring reset	574351	VUVG-L10-M52-MT-M5-1P3
		566466	VUVG-L10-M52-RZT-M5-1P3
		574355	VUVG-L10-M52-MZT-M5-1P3

## Ordering data

Ordering data		Description	Part no.	Type	
<b>In-line valve M5, without E-box</b>					
	<b>5/2-way double solenoid valve</b>				
	Internal pilot air supply		566458	VUVG-L10-B52-T-M5-1P3	
	External pilot air supply		566467	VUVG-L10-B52-ZT-M5-1P3	
	<b>5/3-way valve</b>				
	Internal pilot air supply	Mid-position closed, mechanical spring reset	566459	VUVG-L10-P53C-T-M5-1P3	
		Mid-position exhausted, mechanical spring reset	566460	VUVG-L10-P53E-T-M5-1P3	
		Mid-position pressurised, mechanical spring reset	566461	VUVG-L10-P53U-T-M5-1P3	
	External pilot air supply	Mid-position closed, mechanical spring reset	566468	VUVG-L10-P53C-ZT-M5-1P3	
		Mid-position exhausted, mechanical spring reset	566469	VUVG-L10-P53E-ZT-M5-1P3	
		Mid-position pressurised, mechanical spring reset	566470	VUVG-L10-P53U-ZT-M5-1P3	
<b>In-line valve M5, with E-box R8</b>					
	<b>2x 3/2-way valve</b>				
	Internal pilot air supply	Normally closed, pneumatic spring reset	577347	VUVG-L10-T32C-AT-M5-1R8L	
		Normally open, pneumatic spring reset	8031466	VUVG-L10-T32U-AT-M5-1R8L	
		1x normally open, 1x normally closed, pneumatic spring reset	8031467	VUVG-L10-T32H-AT-M5-1R8L	
		Normally closed, mechanical spring reset	8031468	VUVG-L10-T32C-MT-M5-1R8L	
		Normally open, mechanical spring reset	8031469	VUVG-L10-T32U-MT-M5-1R8L	
		1x normally open, 1x normally closed, mechanical spring reset	8031470	VUVG-L10-T32H-MT-M5-1R8L	
	<b>5/2-way single solenoid valve</b>				
	Internal pilot air supply	Pneumatic/mechanical spring reset	572634	VUVG-L10-M52-RT-M5-1R8L	
		Mechanical spring reset	8031472	VUVG-L10-M52-MT-M5-1R8L	
<b>5/2-way double solenoid valve</b>					
Internal pilot air supply		576664	VUVG-L10-B52-T-M5-1R8L		
<b>5/3-way valve</b>					
Internal pilot air supply	Mid-position exhausted, mechanical spring reset	8031475	VUVG-L10-P53E-T-M5-1R8L		
	Mid-position pressurised, mechanical spring reset	8031476	VUVG-L10-P53U-T-M5-1R8L		
<b>In-line valve M5, with E-box H2</b>					
	<b>5/2-way single solenoid valve</b>				
	Internal pilot air supply	Pneumatic/mechanical spring reset	577316	VUVG-L10-M52-RT-M5-1H2L-W1	
		Mechanical spring reset	578162	VUVG-L10-M52-MT-M5-1H2L-W1	
		<b>5/2-way double solenoid valve</b>			
Internal pilot air supply		577317	VUVG-L10-B52-T-M5-1H2L-W1		
<b>Semi in-line valve M5, with E-box H2</b>					
	<b>5/2-way single solenoid valve</b>				
	Internal pilot air supply	Pneumatic/mechanical spring reset	577324	VUVG-S10-M52-RT-M5-1H2L-W1	

# Solenoid valves VUVG-L10 and VUVG-S10, in-line valves M7

## Data sheet

### Function

2x 3/2C, 2x 3/2U, 2x 3/2H

5/2-way, single solenoid

5/2-way, double solenoid valve


5/3C, 5/3U, 5/3E

-  - Size 10 mm

-  - Flow rate  
170 ... 340 l/min

-  - Voltage  
5, 12 and 24 V DC

Circuit symbols → page 13



### General technical data VUVG-L M7

Valve function	T32-A	T32-M			M52-R	B52	M52-M	P53																		
Normal position	C <sup>1)</sup>	U <sup>2)</sup>	H <sup>4)</sup>	C <sup>1)</sup>	U <sup>2)</sup>	H <sup>4)</sup>	-	-	-	C <sup>1)</sup>	U <sup>2)</sup>	E <sup>3)</sup>														
Stable position	Monostable						Bistable	Monostable	Monostable																	
Pneumatic spring reset	Yes	No			Yes <sup>5)</sup>	-	No	-	-																	
Mechanical spring reset	No	Yes			Yes <sup>5)</sup>	-	Yes	Yes	Yes																	
Vacuum operation at port 1	No	Only with external pilot air supply																								
Design	Piston spool																									
Sealing principle	Soft																									
Type of actuation	Electrical																									
Type of control	Piloted																									
Pilot air supply	Internal or external																									
Exhaust function	Can be throttled																									
Manual override	Choice of non-detenting, covered, non-detenting/detenting or detenting																									
Type of mounting	Optionally via through-holes <sup>6)</sup> or on manifold rail																									
Mounting position	Any																									
Nominal width	[mm]	2.7	2.0	1.9	1.9	4.0		2.8		3.5																
Standard nominal flow rate	[l/min]	190	150	140	140	330	380	220		320																
Flow rate on manifold rail	[l/min]	170	140	130	130	330	340	220		300																
Switching time on/off	[ms]	6/15	8/11			7/17	-	8/24		11/30																
Switching time changeover	[ms]	-				7				14																
Size	[mm]	10																								
Connection	1, 2, 3, 4, 5 12/14	M7 M3																								
Product weight	[g]	55	54		45	55	44	55																		
Certification	c UL us - Recognized (OL) RCM compliance mark																									
CE marking (see declaration of conformity) <sup>7)</sup>	To EU EMC Directive																									
Corrosion resistance class CRC <sup>8)</sup>	2																									

1) C=Normally closed/mid-position closed

2) U=Normally open/mid-position pressurised

3) E=Mid-position exhausted

4) H=2x 3/2-way valve in one housing with 1x normally closed and 1x normally open

5) Combined reset method

6) If several valves are to be screwed together via the through-holes to form a block, a minimum distance of 0.3 mm must be ensured by placing spacer discs between them.

7) For information about the area of use, see the EC declaration of conformity at: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/) → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

8) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

## Data sheet

Operating and environmental conditions			T32-A <sup>1)</sup>	T32-M <sup>3)</sup>	M52-R <sup>2)</sup>	B52	M52-M <sup>3)</sup>	P53
Valve function								
Operating medium		Compressed air to ISO 8573-2010 [7:4:4]						
Operating pressure	Internal	[MPa]	0.15 ... 0.8	0.25 ... 0.8	0.25 ... 0.8	0.15 ... 0.8	0.3 ... 0.8	
		[bar]	1.5 ... 8	2.5 ... 8	2.5 ... 8	1.5 ... 8	3 ... 8	
	External	[MPa]	0.15 ... 1	−0.09 ... 1			−0.09 ... 0.8	−0.09 ... 1
		[bar]	1.5 ... 10	−0.9 ... 10			−0.9 ... 8	−0.9 ... 10
Pilot pressure	[MPa]	0.15 ... 0.8	0.2 ... 0.8	0.25 ... 0.8	0.15 ... 0.8	0.3 ... 0.8	0.3 ... 0.8	
	[bar]	1.5 ... 8	2 ... 8	2.5 ... 8	1.5 ... 8	3 ... 8	3 ... 8	
Ambient temperature	[°C]	−5 ... +50, with holding current reduction −5 ... +60						
Temperature of medium	[°C]	−5 ... +50, with holding current reduction −5 ... +60						

1) Pneumatic spring

2) Mixed, pneumatic/mechanical spring

3) Mechanical spring

### Electrical data

Electrical connection	Via E-box → page 102
Operating voltage	[V DC] 5, 12, 24 ±10%
Power	[W] 1, reduced to 0.35 with holding current reduction
Duty cycle	[%] 100
Degree of protection to EN 60529	IP40 (with plug socket), IP65 (with M8)

### Information on materials



Housing	Wrought aluminium alloy
Seals	HNBR, NBR
Note on materials	RoHS-compliant

## Data sheet


### Dimensions

2x 3/2-way, 5/2-way and 5/3-way valve

Download CAD data → [www.festo.com](http://www.festo.com)



**Note**  
Additional dimensions  
E-boxes  
→ Page 104



[1] Vertical electrical connection

[2] Horizontal electrical connection

[3] Manual override



[4] Port for external pilot air supply

Type	B1	B2	D1	D2	D3	H1	H2	H3	L1	L2	L3	L4
VUVG-L-10 ....-M7...	10.2	-	M7	3.2	M3	32.5	3.6	4.4	86.5	81.5	8	27
VUVG-S-10 ....-M7...												

Type	L5	L6	L7	L8	L9	L10	L11	L12	L13	L14
VUVG-L-10 ....-M7...	4.85	6.15	47	14	11	12	19	-	69.2	66.7
VUVG-S-10 ....-M7...										






## Ordering data

### ★ Core product range

Ordering data		Description	Part no.	Type
<b>In-line valve M7, with E-box R8</b>				
	<b>5/3-way valve</b>	Internal pilot air supply Mid-position closed, mechanical spring reset	★ 574223	VUVG-L10-P53C-T-M7-1R8L
<b>In-line valve M7, without E-box</b>				
	<b>2x 3/2-way valve</b>	Internal pilot air supply Normally closed, pneumatic spring reset Normally open, pneumatic spring reset 1x normally open, 1x normally closed, pneumatic spring reset Normally closed, mechanical spring reset Normally open, mechanical spring reset 1x normally open, 1x normally closed, mechanical spring reset	566471 566472 566473 574356 574357 574358	VUVG-L10-T32C-AT-M7-1P3 VUVG-L10-T32U-AT-M7-1P3 VUVG-L10-T32H-AT-M7-1P3 VUVG-L10-T32C-MT-M7-1P3 VUVG-L10-T32U-MT-M7-1P3 VUVG-L10-T32H-MT-M7-1P3
	External pilot air supply	Normally closed, pneumatic spring reset Normally open, pneumatic spring reset 1x normally open, 1x normally closed, pneumatic spring reset Normally closed, mechanical spring reset Normally open, mechanical spring reset Normally closed, mechanical spring reset	566479 566480 566481 574360 574361 574362	VUVG-L10-T32C-AZT-M7-1P3 VUVG-L10-T32U-AZT-M7-1P3 VUVG-L10-T32H-AZT-M7-1P3 VUVG-L10-T32C-MZT-M7-1P3 VUVG-L10-T32U-MZT-M7-1P3 VUVG-L10-T32H-MZT-M7-1P3

## Solenoid valves VUVG-L10 and VUVG-S10, in-line valves M7

### Ordering data

Ordering data		Description	Part no.	Type
<b>In-line valve M7, without E-box</b>				
	<b>5/2-way single solenoid valve</b>			
	Internal pilot air supply	Mechanical spring reset	574359	VUVG-L10-M52-MT-M7-1P3
		Pneumatic/mechanical spring reset	566474	VUVG-L10-M52-RT-M7-1P3
	External pilot air supply	Mechanical spring reset	574363	VUVG-L10-M52-MZT-M7-1P3
		Pneumatic/mechanical spring reset	566482	VUVG-L10-M52-RZT-M7-1P3
	<b>5/2-way double solenoid valve</b>			
	Internal pilot air supply		566475	VUVG-L10-B52-T-M7-1P3
	External pilot air supply		566483	VUVG-L10-B52-ZT-M7-1P3
	<b>5/3-way valve</b>			
	Internal pilot air supply	Mid-position closed, mechanical spring reset	566476	VUVG-L10-P53C-T-M7-1P3
		Mid-position exhausted, mechanical spring reset	566477	VUVG-L10-P53E-T-M7-1P3
		Mid-position pressurised, mechanical spring reset	566478	VUVG-L10-P53U-T-M7-1P3
	External pilot air supply	Mid-position closed, mechanical spring reset	566484	VUVG-L10-P53C-ZT-M7-1P3
		Mid-position exhausted, mechanical spring reset	566485	VUVG-L10-P53E-ZT-M7-1P3
		Mid-position pressurised, mechanical spring reset	566486	VUVG-L10-P53U-ZT-M7-1P3
	<b>2x 3/2-way valve</b>			
	Internal pilot air supply	Normally closed, pneumatic spring reset	574218	VUVG-L10-T32C-AT-M7-1R8L
		Normally open, pneumatic spring reset	574219	VUVG-L10-T32U-AT-M7-1R8L
		1x normally open, 1x normally closed, pneumatic spring reset	574220	VUVG-L10-T32H-AT-M7-1R8L
		Normally closed, mechanical spring reset	8031480	VUVG-L10-T32C-MT-M7-1R8L
		Normally open, mechanical spring reset	8031481	VUVG-L10-T32U-MT-M7-1R8L
		1x normally open, 1x normally closed, mechanical spring reset	8031482	VUVG-L10-T32H-MT-M7-1R8L
	<b>5/2-way single solenoid valve</b>			
	Internal pilot air supply	Pneumatic/mechanical spring reset	574221	VUVG-L10-M52-RT-M7-1R8L
		Mechanical spring reset	8031485	VUVG-L10-M52-MT-M7-1R8L
	<b>5/2-way double solenoid valve</b>			
	Internal pilot air supply		574222	VUVG-L10-B52-T-M7-1R8L
	<b>5/3-way valve</b>			
	Internal pilot air supply	Mid-position exhausted, mechanical spring reset	574225	VUVG-L10-P53E-T-M7-1R8L
		Mid-position pressurised, mechanical spring reset	574224	VUVG-L10-P53U-T-M7-1R8L
	<b>5/2-way single solenoid valve</b>			
	Internal pilot air supply	Pneumatic/mechanical spring reset	577333	VUVG-L10-M52-RT-M7-1H2L-W1
		Mechanical spring reset	578163	VUVG-L10-M52-MT-M7-1H2L-W1
	<b>5/2-way double solenoid valve</b>			
	Internal pilot air supply		577332	VUVG-L10-B52-T-M7-1H2L-W1


## Manifold assembly

## In-line valves for manifold assembly



## Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)




- |   |  |   |                                      |
|---|--|---|--------------------------------------|
| [1] Ports 1, 3 and 5: G1/8                            | [6] H-rail mounting (two M4x20 screws are required for mounting) | [8] Supply plate  | [10] Vertical pressure supply plate  |
| [2] Ports 1, 2, 3, 4 and 5 on the valve: M7 or M5     |  | [9] Valves/cover plate mounting on manifold rail: M2 thread | [11] Vertical pressure exhaust plate |
| [5] Electrical connection for E-boxes and accessories | [7] Cover plate  |   |                                      |

Type	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12
VABML-L1-10S-G18	94.3	41	24.5	8	52.1	16.5	16	33.7	44.6	40.7	36.7	14.4

Type	D1	D2	D5	H1	H2	H3	H4	H5	H6	H7	H8	L3	L4	L5	L6	L7
VABML-L1-10S-G18	G1/8	4.5	8	80.6	16.8	9.8	64.9	49.3	17.8	18	5.9	5	15	10.5	10.3	2

Valve positions	2	3	4	5	6	7	8	9	10	12	14	16	22
L1	40.5	51	61.5	72	82.5	93	103.5	114	124.5	145.5	166.5	187.5	250.5
L2	30.5	41	51.5	62	72.5	83	93.5	104	114.5	135.5	156.5	177.5	240.5
VABM weight [g]	63	78	93	108	123	138	153	168	183	213	243	273	363


## Ordering data

Technical data – Manifold rails		Connection	CRC	Material <sup>2)</sup>	Operating pressure		Max. tightening torque for assembly [Nm]		
		1, 3, 5			[MPa]	[bar]	Valve	H-rail	Wall
	G1/8	2 <sup>1)</sup>	Wrought aluminium alloy	0.15 ... 0.8	-0.9 ... 10	0.45	1.5	3	





1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

2) Note on materials: RoHS-compliant.

Ordering data – Manifold rail		Description	Part no.	Type
<b>Manifold rail for in-line valve (manifold assembly)</b>				
	For size M5/M7	2 valve positions	★ 566558	VABM-L1-10S-G18-2
		3 valve positions	★ 566559	VABM-L1-10S-G18-3
		4 valve positions	★ 566560	VABM-L1-10S-G18-4
		5 valve positions	566561	VABM-L1-10S-G18-5
		6 valve positions	★ 566562	VABM-L1-10S-G18-6
		7 valve positions	566563	VABM-L1-10S-G18-7
		8 valve positions	★ 566564	VABM-L1-10S-G18-8
		9 valve positions	566565	VABM-L1-10S-G18-9
		10 valve positions	★ 566566	VABM-L1-10S-G18-10
		12 valve positions	566567	VABM-L1-10S-G18-12
		14 valve positions	566568	VABM-L1-10S-G18-14
		16 valve positions	566569	VABM-L1-10S-G18-16

## Ordering data

Ordering data – Accessories		Description	Part no.	Type
Cover plate				Data sheets → Internet: vabb
	For valve position on manifold rail, including screws and seal	★ 566462	VABB-L1-10-S	
Separator				Data sheets → Internet: vabd
	For creating pressure zones	569995	VABD-8-B	
Supply plate				Data sheets → Internet: vabf
	For valve position (in-line valves M5) on manifold rail, including screws and seal	569991	VABF-L1-10-P3A4-M5	
	For valve position (in-line valves M7) on manifold rail, including screws and seal	569992	VABF-L1-10-P3A4-M7	
Seals				Data sheets → Internet: vabd
	<b>In-line valves VUVG-LK</b>			
	For in-line valves M5	Delivery quantity: 10 sets (each with 2 screws and 1 seal)	★ 8043718	VABD-L1-10XK-S-M5-S
	For in-line valves M7		★ 8043719	VABD-L1-10XK-S-M7-S
	<b>In-line valves VUVG-L</b>			
	For in-line valves M5	Delivery quantity: 10 sets (each with 2 screws and 1 seal)	★ 566672	VABD-L1-10X-S-M5
	For in-line valves M7		★ 566673	VABD-L1-10X-S-M7
Vertical pressure supply plate				
	Pneumatic connection 1: M7	Terminal code CP	574592	VABF-L1-P3A3-M7
Vertical pressure exhaust plate				
	Pneumatic connection 3, 5: M7	Terminal code CR	574594	VABF-L1-P7A13-M7


# Solenoid valves VUVG-LK14, in-line valves G1/8

## Data sheet

Function  
2x 3/2C  
5/2-way, single solenoid  
5/2-way, double solenoid valve

Circuit symbols → page 13

-  - Size 14 mm
-  - Flow rate  
570 ... 660 l/min
-  - Voltage  
24 V DC



### General technical data VUVG-LK

Valve function	T32-A	M52-A	B52
Normal position	C <sup>1)</sup>	-	-
Stable position	Monostable		Bistable
Pneumatic spring reset	Yes	Yes	-
Design	Piston spool		
Sealing principle	Soft		
Type of actuation	Electrical		
Type of control	Piloted		
Pilot air supply	Internal		
Exhaust function	Can be throttled		
Manual override	Non-detenting, detenting		
Type of mounting	Optionally via through-holes <sup>2)</sup> or on manifold rail		
Mounting position	Any		
Standard nominal flow rate	[l/min]	570	660
Switching time on/off	[ms]	13/20	14/24
Switching time changeover	[ms]	-	8
Size	[mm]	14	
Connection	2, 4	G1/8	
Product weight	[g]	75	65
Corrosion resistance class CRC <sup>3)</sup>		2	85

1) C=Normally closed

2) If several valves are to be screwed together via the through-holes to form a block, a minimum distance of 0.3 mm must be ensured by placing spacer discs between them.

3) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

### Safety data

Max. positive test pulse with 0 signal	[μs]	1600
Max. negative test pulse with 1 signal	[μs]	3000
Shock resistance		Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27
Vibration resistance		Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6


## Data sheet

Operating and environmental conditions			
Valve function	T32-A <sup>1)</sup>	M52-A <sup>1)</sup>	B52
Operating medium	Compressed air to ISO 8573-2010 [7:4:4]		
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)		
Operating pressure	[MPa]	0.15 ... 0.7	0.25 ... 0.7
	[bar]	1.5 ... 7	2.5 ... 7
Ambient temperature	[°C]	-5 ... +50	1.5 ... 7
Temperature of medium	[°C]	-5 ... +50	


1) Pneumatic spring

Electrical data			
Electrical connection	Via E-box → page 102		
Operating voltage	[V DC]	24 ±10%	
Power	[W]	0.7	
Duty cycle	[%]	100	
Degree of protection to EN 60529		IP40 (with plug socket), IP65 (with M8)	
Signal status display		LED	
Maximum switching frequency	[Hz]	2	

Information on materials			
Housing		Wrought aluminium alloy	
Seals		HNBR, NBR	
Note on materials		RoHS-compliant	
		Contains paint-wetting impairment substances	

Pin allocation for E-box			
	Pin		Description
Rectangular plug, connection pattern H			
	1	+ or -	Protective circuit without holding current reduction
	2	+ or -	
Round plug, M8, 3-pin	1	Not used	Protective circuit without holding current reduction
	3	+ or -	
	4	+ or -	

### Protective circuit without holding current reduction




The solenoid coils have a protective circuit to arrest sparks and protect against polarity reversal.


## Data sheet

## Dimensions

2x 3/2-way, 5/2-way valve, double solenoid



5/2-way single solenoid valve

Download CAD data → [www.festo.com](http://www.festo.com)

Note

Additional dimensions

E-boxes

→ Page 104

[2] Horizontal electrical connection



[3] Manual override

Type	B1	D1	D2	H1	H3	L1	L2	L3	L4	L5
VUVG-LK14-T32C...-G18...	14.4	G1/8	3.3	34.8	3.2	118.9	116.4	41	37	39.7
VUVG-LK14-B52...-G18...										
VUVG-LK14-M52...-G18...						95.6	94.4			17.7

Type	L7	L8	L9	L10	L11
VUVG-LK14-T32C...-G18...	66.5	18.4	14.9	17	24.8
VUVG-LK14-B52...-G18...					
VUVG-LK14-M52...-G18...					

## Ordering data

### ★ Core product range

Ordering data		Description	Part no.	Type
<b>In-line valve G1/8, with E-box R8</b>				
	<b>2x 3/2-way valve</b>			
	Internal pilot air supply	Normally closed, pneumatic spring reset	★ 8042566	VUVG-LK14-T32C-AT-G18-1R8L-S
	<b>5/2-way single solenoid valve</b>			
	Internal pilot air supply	Pneumatic spring reset	★ 8042567	VUVG-LK14-M52-AT-G18-1R8L-S
<b>5/2-way double solenoid valve</b>				
Internal pilot air supply		★ 8042568	VUVG-LK14-B52-T-G18-1R8L-S	
<b>In-line valve G1/8, with E-box H2</b>				
	<b>2x 3/2-way valve</b>			
	Internal pilot air supply	Normally closed, pneumatic spring reset	★ 8042562	VUVG-LK14-T32C-AT-G18-1H2L-S
	<b>5/2-way single solenoid valve</b>			
	Internal pilot air supply	Pneumatic spring reset	★ 8042563	VUVG-LK14-M52-AT-G18-1H2L-S
<b>5/2-way double solenoid valve</b>				
Internal pilot air supply		★ 8042564	VUVG-LK14-B52-T-G18-1H2L-S	

## Data sheet

### Function

2x 3/2C, 2x 3/2U, 2x 3/2H

5/2-way, single solenoid

5/2-way, double solenoid valve

5/3C, 5/3U, 5/3E

- - Size 14 mm

- - Flow rate  
480 ... 780 l/min

- - Voltage  
5, 12 and 24 V DC

Circuit symbols → page 13



### General technical data VUVG-L

Valve function	T32-A	T32-M			M52-A	B52	M52-M	P53															
Normal position	C <sup>1)</sup>	U <sup>2)</sup>	H <sup>4)</sup>	C <sup>1)</sup>	U <sup>2)</sup>	H <sup>4)</sup>	-	-															
Stable position	Monostable				Bistable		Monostable																
Pneumatic spring reset	Yes		No		Yes		-	No															
Mechanical spring reset	No		Yes		No		-	Yes															
Vacuum operation at port 1	No		Only with external pilot air supply																				
Size [mm]	14																						
Design	Piston spool																						
Sealing principle	Soft																						
Type of actuation	Electrical																						
Type of control	Piloted																						
Pilot air supply	Internal or external																						
Exhaust function	Can be throttled																						
Manual override	VUVG-...	Choice of non-detenting, covered, non-detenting/detenting or detenting																					
	VUVG-...-P1	Non-detenting, non-detenting/detenting																					
Type of mounting	Optionally via through-holes <sup>5)</sup> or on manifold rail																						
Mounting position	Any																						
Nominal width [mm]	4.6		4.3		5.6	5.6	5.6	5.6															
Standard nominal flow rate [l/min]	560	600	590	550	500	500	780	780															
Flow rate on manifold rail [l/min]	560	580		520	480	480	680	700															
<b>Switching time</b>																							
VUVG-...	On/off	[ms]	9/25	12/18		14/22	-	13/37															
	Changeover	[ms]	-			8	-	14															
VUVG-...-P1	On/off	11/18		14/13		16/16	-	12/26															
	Changeover	-	-		-	12	-	19															
Pneumatic connection	1, 2, 3, 4, 5	G1/8																					
	12/14	M5																					

1) C=Normally closed/mid-position closed

2) U=Normally open/mid-position pressurised

3) E=Mid-position exhausted

4) H=2x 3/2-way valve in one housing with 1x normally closed and 1x normally open

5) If several valves are to be screwed together via the through-holes to form a block, a minimum distance of 0.3 mm must be ensured by placing spacer discs between them.

## Data sheet

General technical data VUVG-L							
Valve function	T32-A	T32-M	M52-A	B52	M52-M	P53	
Product weight	VUVG-... [g] 89 VUVG-...-P1 [g] 65	80	78	89	70	89	
Certification for VUVG-...	c UL us - Recognized (OL) RCM						
CE marking (see declaration of conformity) <sup>1)</sup>							
VUVG-...	To EU EMC Directive						
VUVG-...-P1	To EU Low Voltage Directive						
Corrosion resistance class CRC <sup>2)</sup>	2						

- 1) For information about the area of use, see the EC declaration of conformity at: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/) → Support/Downloads.  
If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.
- 2) Corrosion resistance class CRC 2 to Festo standard FN 940070  
Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

Operating and environmental conditions		T32-A <sup>1)</sup>	T32-M <sup>2)</sup>	M52-A <sup>1)</sup>	B52	M52-M <sup>2)</sup>	P53	
Valve function		Compressed air to ISO 8573-2010 [7:4:4]						
Operating pressure	Internal	[MPa]	0.15 ... 0.8	0.25 ... 0.8	0.15 ... 0.8	0.3 ... 0.8	0.3 ... 0.8	
		[bar]	1.5 ... 8	3 ... 8	2.5 ... 8	1.5 ... 8	3 ... 8	
	External VUVG-...	[MPa]	0.15 ... 1	-0.09 ... 1		-0.09 ... 0.8	-0.09 ... 1	
		[bar]	1.5... 10	-0.9... 10		-0.9... 8	-0.9... 10	
Pilot pressure <sup>3)</sup>	Internal	[MPa]	0.15 ... 0.8	0.35 ... 0.8	0.25 ... 0.8	0.15 ... 0.8	0.3 ... 0.8	
		[bar]	1.5 ... 8	3.5 ... 8	2.5 ... 8	1.5 ... 8	3 ... 8	
	External VUVG-...	[MPa]	0.15 ... 0.8	0.3 ... 0.8	0.25 ... 0.8	0.15 ... 0.8	0.3 ... 0.8	
		[bar]	1.5 ... 8	3 ... 8	2.5 ... 8	1.5 ... 8	3 ... 8	
Ambient temperature		VUVG-...	-5 ... +50, with holding current reduction -5 ... +60					
		VUVG-...-P1	-5 ... +50 for mounting on manifold rail, -5 ... +60					
Temperature of medium		VUVG-...	-5 ... +50, with holding current reduction -5 ... +60					
		VUVG-...-P1	-5 ... +50, for mounting on manifold rail, -5 ... +60					

- 1) Pneumatic spring  
2) Mechanical spring  
3) Minimum pilot pressure 50% of operating pressure

Electrical data		
Electrical connection	VUVG-...	Via E-box → page 104
	VUVG-...-P1	Via electric pilot valve
Pilot interface	VUVG-...-P1	To ISO 15218
Operating voltage	VUVG-...	[V DC] 5, 12 and 24 ±10%
	VUVG-...-P1	[V DC] 12 and 24 ±10%
		[V AC] 24, 110 and 230 ±10%
Power	VUVG-...	[W] 1, reduced to 0.35 with holding current reduction
	VUVG-...-P1	[W] 1.3
Duty cycle ED	[%]	100
Degree of protection to EN 60529	VUVG-...	IP40 (with plug socket), IP65 (with M8)
	VUVG-...-P1	IP65, with electric pilot valve and plug socket

Safety data		
Max. positive test pulse with 0 signal	[μs]	700
Max. negative test pulse with 1 signal	[μs]	900
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance		Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6



Information on materials	
Housing	Wrought aluminium alloy
Seals	HNBR, NBR
Note on materials	RoHS-compliant

## Data sheet


### Dimensions VUVG

2x 3/2-way, 5/2-way and 5/3-way valve

Download CAD data → [www.festo.com](http://www.festo.com)



Note  
Additional dimensions  
E-boxes  
→ Page 104



[1] Horizontal electrical connection

[2] Manual override

[3] Port for external pilot air supply

Type	B1	B2	D1	D2 Ø	D3	H1	H2	L1	L2	L3	L4	L5	L6
VUVG-L14 ....G18...	14.4	2.3	G1/8	3.2	-	34.8	5.8	107	102	8	37	4.85	6.2
VUVG-S14 ....G18...													

Type	L7	L8	L9	L10	L11	L12	L13	L14	L15
VUVG-L14 ....G18...	66.5	18.35	14.9	18	24.3	13.5	10.8	89.4	87
VUVG-S14 ....G18...									


## Data sheet

## Dimensions VUVG-...-P1

2x 3/2-way, 5/2-way and 5/3-way valve

Download CAD data → [www.festo.com](http://www.festo.com)

5/2-way valve, single solenoid




[2] Ports 1...5


[3] Port for external pilot air supply

Type	B1	D1	D2 ∅	H2	H3	L1	L2	L3	L4	L5	L6	L7	L8	L9	L11	L12
VUVG-L14-...-P1	14.4	G1/8	3.2	34.8	23.2	105.2	66.5	33.1	37	24.3	18	14.9	14.9	18.4	88.6	16.5







## Ordering data

## ★ Core product range


Ordering data	Description	Part no.	Type
<b>In-line valve G1/8, with E-box R8</b>			
	<b>5/3-way valve</b> Internal pilot air supply Mid-position closed, mechanical spring reset	★ 574231	VUVG-L14-P53C-T-G18-1R8L

Ordering data	Description	Part no.	Type
<b>In-line valve G1/8, without E-box</b>			
	<b>2x 3/2-way valve</b> Internal pilot air supply Normally closed, pneumatic spring reset Normally open, pneumatic spring reset 1x normally open, 1x normally closed, pneumatic spring reset Normally closed, mechanical spring reset Normally open, mechanical spring reset 1x normally open, 1x normally closed, mechanical spring reset	566496 566497 566498 574368 574369 574370	VUVG-L14-T32-AT-G18-P3 VUVG-L14-32U-AT-G18-1P3 VUVG-L14-T32H-AT-G18-1P3 VUVG-L14-T32C-MT-G18-1P3 VUVG-L14-T32U-MT-G18-1P3 VUVG-L14-T32H-MT-G18-1P3
	External pilot air supply Normally closed, pneumatic spring reset Normally open, pneumatic spring reset 1x normally open, 1x normally closed, pneumatic spring reset Normally closed, mechanical spring reset Normally open, mechanical spring reset Normally closed, mechanical spring reset	566505 566506 566507 574372 574373 574374	VUVG-L14-T32C-AZT-G18-1P3 VUVG-L14-T32U-AZT-G18-1P3 VUVG-L14-T32H-AZT-G18-1P3 VUVG-L14-T32C-MZT-G18-1P3 VUVG-L14-T32U-MZT-G18-1P3 VUVG-L14-T32H-MZT-G18-1P3
	<b>5/2-way single solenoid valve</b> Internal pilot air supply Pneumatic spring reset Mechanical spring reset	566499 574371	VUVG-L14-M52-AT-G18-1P3 VUVG-L14-M52-MT-G18-1P3
	External pilot air supply Pneumatic spring return Mechanical spring reset	566508 574375	VUVG-L14-M52-AZT-G18-1P3 VUVG-L14-M52-MZT-G18-1P3
	<b>5/2-way double solenoid valve</b> Internal pilot air supply External pilot air supply	566500 566509	VUVG-L14-B52-T-G18-1P3 VUVG-L14-B52-ZT-G18-1P3

## Ordering data

Ordering data		Description	Part no.	Type																																										
<b>In-line valve G1/8, without E-box</b>																																														
 <b>5/3-way valve</b> <table border="1"> <tr> <td>Internal pilot air supply</td> <td>Mid-position closed, mechanical spring reset</td> <td>566501</td> <td>VUVG-L14-P53C-T-G18-1P3</td> </tr> <tr> <td></td> <td>Mid-position exhausted, mechanical spring reset</td> <td>566502</td> <td>VUVG-L14-P53E-T-G18-1P3</td> </tr> <tr> <td></td> <td>Mid-position pressurised, mechanical spring reset</td> <td>566503</td> <td>VUVG-L14-P53U-T-G18-1P3</td> </tr> <tr> <td rowspan="3">External pilot air supply</td><td>Mid-position closed, mechanical spring reset</td> <td>566510</td> <td>VUVG-L14-P53C-ZT-G18-1P3</td> </tr> <tr> <td>Mid-position exhausted, mechanical spring reset</td> <td>566511</td> <td>VUVG-L14-P53E-ZT-G18-1P3</td> </tr> <tr> <td>Mid-position pressurised, mechanical spring reset</td> <td>566512</td> <td>VUVG-L14-P53U-ZT-G18-1P3</td> </tr> </table>					Internal pilot air supply	Mid-position closed, mechanical spring reset	566501	VUVG-L14-P53C-T-G18-1P3		Mid-position exhausted, mechanical spring reset	566502	VUVG-L14-P53E-T-G18-1P3		Mid-position pressurised, mechanical spring reset	566503	VUVG-L14-P53U-T-G18-1P3	External pilot air supply	Mid-position closed, mechanical spring reset	566510	VUVG-L14-P53C-ZT-G18-1P3	Mid-position exhausted, mechanical spring reset	566511	VUVG-L14-P53E-ZT-G18-1P3	Mid-position pressurised, mechanical spring reset	566512	VUVG-L14-P53U-ZT-G18-1P3																				
Internal pilot air supply	Mid-position closed, mechanical spring reset	566501	VUVG-L14-P53C-T-G18-1P3																																											
	Mid-position exhausted, mechanical spring reset	566502	VUVG-L14-P53E-T-G18-1P3																																											
	Mid-position pressurised, mechanical spring reset	566503	VUVG-L14-P53U-T-G18-1P3																																											
External pilot air supply	Mid-position closed, mechanical spring reset	566510	VUVG-L14-P53C-ZT-G18-1P3																																											
	Mid-position exhausted, mechanical spring reset	566511	VUVG-L14-P53E-ZT-G18-1P3																																											
	Mid-position pressurised, mechanical spring reset	566512	VUVG-L14-P53U-ZT-G18-1P3																																											
<b>In-line valve G1/8, with E-box R8</b>																																														
 <b>2x 3/2-way valve</b> <table border="1"> <tr> <td>Internal pilot air supply</td> <td>Normally closed, pneumatic spring reset</td> <td>574226</td> <td>VUVG-L14-T32C-AT-G18-1R8L</td> </tr> <tr> <td></td> <td>Normally open, pneumatic spring reset</td> <td>574227</td> <td>VUVG-L14-T32U-AT-G18-1R8L</td> </tr> <tr> <td></td> <td>1x normally open, 1x normally closed, pneumatic spring reset</td> <td>574228</td> <td>VUVG-L14-T32H-AT-G18-1R8L</td> </tr> <tr> <td rowspan="3">Internal pilot air supply</td><td>Normally closed, mechanical spring reset</td> <td>8031504</td> <td>VUVG-L14-T32C-MT-G18-1R8L</td> </tr> <tr> <td>Normally open, mechanical spring reset</td> <td>8031505</td> <td>VUVG-L14-T32U-MT-G18-1R8L</td> </tr> <tr> <td>1x normally open, 1x normally closed, mechanical spring reset</td> <td>8031506</td> <td>VUVG-L14-T32H-MT-G18-1R8L</td> </tr> </table> <b>5/2-way single solenoid valve</b> <table border="1"> <tr> <td>Internal pilot air supply</td> <td>Pneumatic spring reset</td> <td>574229</td> <td>VUVG-L14-M52-AT-G18-1R8L</td> </tr> <tr> <td></td> <td>Mechanical spring reset</td> <td>8031508</td> <td>VUVG-L14-M52-MT-G18-1R8L</td> </tr> </table> <b>5/2-way double solenoid valve</b> <table border="1"> <tr> <td>Internal pilot air supply</td> <td></td> <td>574230</td> <td>VUVG-L14-B52-T-G18-1R8L</td> </tr> </table> <b>5/3-way valve</b> <table border="1"> <tr> <td>Internal pilot air supply</td> <td>Mid-position exhausted, mechanical spring reset</td> <td>574233</td> <td>VUVG-L14-P53E-T-G18-1R8L</td> </tr> <tr> <td></td> <td>Mid-position pressurised, mechanical spring reset</td> <td>574232</td> <td>VUVG-L14-P53U-T-G18-1R8L</td> </tr> </table>					Internal pilot air supply	Normally closed, pneumatic spring reset	574226	VUVG-L14-T32C-AT-G18-1R8L		Normally open, pneumatic spring reset	574227	VUVG-L14-T32U-AT-G18-1R8L		1x normally open, 1x normally closed, pneumatic spring reset	574228	VUVG-L14-T32H-AT-G18-1R8L	Internal pilot air supply	Normally closed, mechanical spring reset	8031504	VUVG-L14-T32C-MT-G18-1R8L	Normally open, mechanical spring reset	8031505	VUVG-L14-T32U-MT-G18-1R8L	1x normally open, 1x normally closed, mechanical spring reset	8031506	VUVG-L14-T32H-MT-G18-1R8L	Internal pilot air supply	Pneumatic spring reset	574229	VUVG-L14-M52-AT-G18-1R8L		Mechanical spring reset	8031508	VUVG-L14-M52-MT-G18-1R8L	Internal pilot air supply		574230	VUVG-L14-B52-T-G18-1R8L	Internal pilot air supply	Mid-position exhausted, mechanical spring reset	574233	VUVG-L14-P53E-T-G18-1R8L		Mid-position pressurised, mechanical spring reset	574232	VUVG-L14-P53U-T-G18-1R8L
Internal pilot air supply	Normally closed, pneumatic spring reset	574226	VUVG-L14-T32C-AT-G18-1R8L																																											
	Normally open, pneumatic spring reset	574227	VUVG-L14-T32U-AT-G18-1R8L																																											
	1x normally open, 1x normally closed, pneumatic spring reset	574228	VUVG-L14-T32H-AT-G18-1R8L																																											
Internal pilot air supply	Normally closed, mechanical spring reset	8031504	VUVG-L14-T32C-MT-G18-1R8L																																											
	Normally open, mechanical spring reset	8031505	VUVG-L14-T32U-MT-G18-1R8L																																											
	1x normally open, 1x normally closed, mechanical spring reset	8031506	VUVG-L14-T32H-MT-G18-1R8L																																											
Internal pilot air supply	Pneumatic spring reset	574229	VUVG-L14-M52-AT-G18-1R8L																																											
	Mechanical spring reset	8031508	VUVG-L14-M52-MT-G18-1R8L																																											
Internal pilot air supply		574230	VUVG-L14-B52-T-G18-1R8L																																											
Internal pilot air supply	Mid-position exhausted, mechanical spring reset	574233	VUVG-L14-P53E-T-G18-1R8L																																											
	Mid-position pressurised, mechanical spring reset	574232	VUVG-L14-P53U-T-G18-1R8L																																											
<b>In-line valve G1/8, with E-box H2</b>																																														
 <b>2x 3/2-way valve</b> <table border="1"> <tr> <td>Internal pilot air supply</td> <td>Normally closed, pneumatic spring reset</td> <td>577321</td> <td>VUVG-L14-T32C-AT-G18-1H2L-W1</td> </tr> </table> <b>5/2-way single solenoid valve</b> <table border="1"> <tr> <td>Internal pilot air supply</td> <td>Pneumatic spring reset</td> <td>576256</td> <td>VUVG-L14-M52-AT-G18-1H2L-W1</td> </tr> <tr> <td></td> <td>Mechanical spring reset</td> <td>578164</td> <td>VUVG-L14-M52-MT-G18-1H2L-W1</td> </tr> </table> <b>5/2-way double solenoid valve</b> <table border="1"> <tr> <td>Internal pilot air supply</td> <td></td> <td>577319</td> <td>VUVG-L14-B52-T-G18-1H2L-W1</td> </tr> </table>					Internal pilot air supply	Normally closed, pneumatic spring reset	577321	VUVG-L14-T32C-AT-G18-1H2L-W1	Internal pilot air supply	Pneumatic spring reset	576256	VUVG-L14-M52-AT-G18-1H2L-W1		Mechanical spring reset	578164	VUVG-L14-M52-MT-G18-1H2L-W1	Internal pilot air supply		577319	VUVG-L14-B52-T-G18-1H2L-W1																										
Internal pilot air supply	Normally closed, pneumatic spring reset	577321	VUVG-L14-T32C-AT-G18-1H2L-W1																																											
Internal pilot air supply	Pneumatic spring reset	576256	VUVG-L14-M52-AT-G18-1H2L-W1																																											
	Mechanical spring reset	578164	VUVG-L14-M52-MT-G18-1H2L-W1																																											
Internal pilot air supply		577319	VUVG-L14-B52-T-G18-1H2L-W1																																											
<b>Semi in-line valve G1/8, with E-box H2</b>																																														
<b>5/2-way single solenoid valve</b> <table border="1"> <tr> <td></td> <td>Internal pilot air supply</td> <td>Pneumatic spring reset</td> <td>577325</td> <td>VUVG-S14-M52-AT-G18-1H2L-W1</td> </tr> </table>						Internal pilot air supply	Pneumatic spring reset	577325	VUVG-S14-M52-AT-G18-1H2L-W1																																					
	Internal pilot air supply	Pneumatic spring reset	577325	VUVG-S14-M52-AT-G18-1H2L-W1																																										

## Ordering data

Ordering data		Description	Part no.	Type
<b>In-line valve G1/8, to ISO 15218</b>				
	<b>2x 3/2-way valve</b>			
	Internal pilot air supply	Normally closed, pneumatic spring reset	8033523	VUVG-L14-T32C-A-G18-P1
		Normally open, pneumatic spring reset	8033524	VUVG-L14-T32U-A-G18-P1
		1x normally open, 1x normally closed, pneumatic spring reset	8033525	VUVG-L14-T32H-A-G18-P1
		Normally closed, mechanical spring reset	8033526	VUVG-L14-T32C-M-G18-P1
		Normally open, mechanical spring reset	8033527	VUVG-L14-T32U-M-G18-P1
		1x normally open, 1x normally closed, mechanical spring reset	8033528	VUVG-L14-T32H-M-G18-P1
<b>5/2-way valve, single solenoid</b>				
Internal pilot air supply	Pneumatic spring reset	8033529	VUVG-L14-M52-A-G18-P1	
	Mechanical spring reset	8033530	VUVG-L14-M52-M-G18-P1	
<b>5/2-way, valve, double solenoid</b>				
Internal pilot air supply	-	8033531	VUVG-L14-B52-G18-P1	
<b>5/3-way valve</b>				
Internal pilot air supply	Mid-position closed, mechanical spring reset	8033532	VUVG-L14-P53C-G18-P1	
	Mid-position exhausted, mechanical spring reset	8033533	VUVG-L14-P53E-G18-P1	
	Mid-position pressurised, mechanical spring reset	8033534	VUVG-L14-P53U-G18-P1	


## Manifold assembly

### In-line valves for manifold assembly





#### Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



Note

Additional dimensions  
E-boxes  
→ Page 104



[1] Ports 1, 3 and 5: G1/4 (at both ends)

[2] Ports 1, 2, 3, 4 and 5 on the valve: G1/8

[5] Electrical connection for E-boxes and accessories

[6] H-rail mounting (two M4x25 screws are required for mounting)

[7] Cover plate

[8] Supply plate, ports 1, 3 and 5: G1/8

[9] Valves/cover plate mounting on manifold rail: M2.5 thread

[10] Vertical pressure supply plate


[11] Vertical pressure exhaust plate

Type	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12	D1	D2
VABM-L1-14S-G14	116.6	56.6	36.5	16.4	72.9	26.5	20	43.5	53.1	48.3	43.5	4.5	G1/4	4.5

Type	H1	H2	H3	H4	H5	H6	H7	H8	L3	L4	L5	L6	L7
VABM-L1-14S-G14	95.3	20	10.6	74.9	54.8	23.9	15.4	6.5	5	17	16	14.5	2

Valve positions	2	3	4	5	6	7	8	9	10	12	14	16	22
L1	50	66	82	98	114	130	146	162	178	210	242	274	306
L2	40	56	72	88	104	120	136	152	168	200	232	264	296
VABM weight [g]	118	159	200	241	282	323	364	405	446	528	610	692	938


## Ordering data

Technical data – Manifold rails				Operating pressure		Max. tightening torque for assembly [Nm]		
	Connection 1, 3, 5	CRC	Material <sup>2)</sup>	[MPa]	[bar]	Valve	H-rail	Wall
	G1/4	2 <sup>1)</sup>	Wrought aluminium alloy	0.15 ... 0.8	-0.9 ... 10	0.65	1.5	3





1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

2) Note on materials: RoHS-compliant.

Ordering data – Manifold rail		Description	Part no.	Type
<b>Manifold rail for in-line valves (manifold assembly)</b>				
	For size G1/8	2 valve positions	 <b>566618</b>	VABM-L1-14S-G14-2
		3 valve positions	 <b>566619</b>	VABM-L1-14S-G14-3
		4 valve positions	 <b>566620</b>	VABM-L1-14S-G14-4
		5 valve positions	<b>566621</b>	VABM-L1-14S-G14-5
		6 valve positions	 <b>566622</b>	VABM-L1-14S-G14-6
		7 valve positions	<b>566623</b>	VABM-L1-14S-G14-7
		8 valve positions	 <b>566624</b>	VABM-L1-14S-G14-8
		9 valve positions	<b>566625</b>	VABM-L1-14S-G14-9
		10 valve positions	 <b>566626</b>	VABM-L1-14S-G14-10
		12 valve positions	<b>566627</b>	VABM-L1-14S-G14-12
		14 valve positions	<b>566628</b>	VABM-L1-14S-G14-14
		16 valve positions	<b>566629</b>	VABM-L1-14S-G14-16

## Ordering data

Ordering data – Accessories		Description	Part no.	Type
Cover plate				Data sheets → Internet: vabb
	For valve position on manifold rail, including screws and seal	★ 569989	VABB-L1-14	
Separator				Data sheets → Internet: vabd
	For creating pressure zones	569996	VABD-10-B	
Supply plate				Data sheets → Internet: vabf
	For valve position on manifold rail, including screws and seal	569993	VABF-L1-14-P3A4-G18	
Seals for in-line valves				Data sheets → Internet: vabd
	<b>In-line valves VUVG-LK</b>			
	For G1/8 in-line valves	Delivery quantity: 10 sets (each with 2 screws and 1 seal)	★ 8043720	VABD-L1-14XK-S-G18-S
	<b>In-line valves VUVG-L</b>			
	For G1/8 in-line valves	Delivery quantity: 10 sets (each with 2 screws and 1 seal)	★ 566675	VABD-L1-14X-S-G18
Vertical pressure supply plate				
	Pneumatic connection 1: G1/8	Terminal code CP	574593	VABF-L1-P3A3-G18
Vertical pressure exhaust plate				
	Pneumatic connection 3, 5: G1/8	Terminal code CR	574595	VABF-L1-P7A13-G18

## Data sheet

### Function

2x 3/2C, 2x 3/2U, 2x 3/2H

5/2-way, single solenoid

5/2-way, double solenoid valve


5/3C, 5/3U, 5/3E

-  - Size 18 mm

-  - Flow rate  
1000 ... 1380 l/min

-  - Voltage  
5, 12 and 24 V DC

Circuit symbols → page 13



### General technical data VUVG-L

Valve function	T32-A	T32-M			M52-R	B52	M52-M	P53																
Normal position	C <sup>1)</sup>	U <sup>2)</sup>	H <sup>4)</sup>	C <sup>1)</sup>	U <sup>2)</sup>	H <sup>4)</sup>	-	-	C <sup>1)</sup>	U <sup>2)</sup>														
Stable position	Monostable					Bistable	Monostable																	
Pneumatic spring reset	Yes		No			Yes <sup>5)</sup>	-	No	-															
Mechanical spring reset	No		Yes			Yes <sup>5)</sup>	-	Yes	Yes															
Vacuum operation at port 1	No		Only with external pilot air supply																					
Size [mm]	18																							
Design	Piston spool																							
Sealing principle	Soft																							
Type of actuation	Electrical																							
Type of control	Piloted																							
Pilot air supply	Internal/external																							
Exhaust function	Can be throttled																							
Manual override	VUVG-...	Choice of non-detenting, covered, non-detenting/detenting or detenting																						
	VUVG-....-P1	Non-detenting, non-detenting/detenting																						
Type of mounting	Optionally via through-holes <sup>6)</sup> or on manifold rail																							
Mounting position	Any																							
Nominal width [mm]	5.7			6.9			7.3	6.9	6.5	6.3														
Standard nominal flow rate [l/min]	880	970	950	870	990	920	1300	1380	1300	1200														
Flow rate on manifold rail	780	980	820	780	960	820	1300	1370	1300	1180														
Switching time																								
VUVG-...	On/off	[ms]	13/27	15/22			15/31	-	10/45	15/48														
	Changeover	[ms]	-	-			-	11	-	29														
VUVG-....-P1	On/off	[ms]	13/18	16/15			16/22	-	14/26	15/32														
	Changeover	[ms]	-	-			-	12	-	21														
Pneumatic connection	1, 2, 3, 4, 5	G1/4																						
	12/14	M5																						
Product weight	VUVG-...	[g]	164	164			154	164	154	160														
	VUVG-....-P1	[g]	140	140			142	140	142	136														
Certification	VUVG-...	c UL us - Recognized (OL)																						
		RCM																						
CE marking (see declaration of conformity) <sup>7)</sup>																								
VUVG-...	To EU EMC Directive																							
VUVG-....-P1	To EU Low Voltage Directive																							
Corrosion resistance class CRC <sup>8)</sup>	2																							

1) C=Normally closed/mid-position closed

2) U=Normally open/mid-position pressurised

3) E=Mid-position exhausted

4) H=2x 3/2-way valve in one housing with 1x normally closed and 1x normally open

5) Combined reset method

6) If several valves are to be screwed together via the through-holes to form a block, a minimum distance of 0.3 mm must be ensured by placing spacer discs between them.

7) For information about the area of use, see the EC declaration of conformity at: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/) → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

8) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

## Data sheet

Operating and environmental conditions								
Valve function		T32-A <sup>1)</sup>	T32-M <sup>3)</sup>	M52-R <sup>2)</sup>	B52	M52-M <sup>3)</sup>	P53	
Operating medium		Compressed air to ISO 8573-2010 [7:4:4]						
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)							
Operating pressure	Internal	[MPa]	0.15 ... 0.8	0.3 ... 0.8	0.25 ... 0.8	0.15 ... 0.8	0.3 ... 0.8	
		[bar]	1.5 ... 8	3 ... 8	2.5 ... 8	1.5 ... 8	3 ... 8	
	External VUVG....	[MPa]	0.15 ... 1	-0.09 ... 1				
		[bar]	1.5 ... 10	-0.9 ... 10				
Pilot pressure <sup>4)</sup>		[MPa]	0.15 ... 0.8	0.2 ... 0.8	0.25 ... 0.8	0.15 ... 0.8	0.3 ... 0.8	
		[bar]	1.5 ... 8	2 ... 8	2.5 ... 8	1.5 ... 8	3 ... 8	
Ambient temperature	VUVG...	[°C]	-5 ... +50, with holding current reduction	-5 ... +60				
	VUVG...-P1	[°C]	-5 ... +50 for mounting on manifold rail, -5 ... +60					
Temperature of medium	VUVG...	[°C]	-5 ... +50, with holding current reduction	-5 ... +60				
	VUVG...-P1	[°C]	-5 ... +50 for mounting on manifold rail, -5 ... +60					

1) Pneumatic spring

2) Mixed, pneumatic/mechanical spring

3) Mechanical spring

4) Minimum pilot pressure 50% of operating pressure

### Electrical data

Electrical connection	VUVG...	Via E-box → page 102
	VUVG...-P1	Via electric pilot valve
Pilot interface	VUVG...-P1	To ISO 15218
Operating voltage	VUVG...	[V DC] 5, 12 and 24 ±10%
	VUVG...-P1	[V DC] 12 and 24 ±10%
		[V AC] 24, 110 and 230 ±10%
Power	VUVG...	[W] 1, reduced to 0.35 with holding current reduction
	VUVG...-P1	[W] 1.3
Duty cycle ED	[%]	100
<b>Degree of protection to EN 60529</b>		
	VUVG...	IP40 (with plug socket), IP65 (with M8)
	VUVG...-P1	IP65, with electric pilot valve and plug socket

### Safety data

Max. positive test pulse with 0 signal	[μs]	700
Max. negative test pulse with 1 signal	[μs]	900
Shock resistance		Shock test with severity level 2 to FN 942017-5 and EN 60068-2-27
Vibration resistance		Transport application test with severity level 2 to FN 942017-4 and EN 60068-2-6

### Information on materials



Housing	Wrought aluminium alloy
Seals	HNBR, NBR
Note on materials	RoHS-compliant

## Data sheet


### Dimensions VUVG-...

2x 3/2-way, 5/2-way and 5/3-way valve

Download CAD data → [www.festo.com](http://www.festo.com)



 **Note**  
Additional dimensions  
E-boxes  
→ Page 104



[1] Electrical connection without  
E-box

[2] Retaining screw

[3] Port for external pilot air supply

Type	B1	B2	D1	D2	D3	H1	H2	H3	L1	L2	L3	L4	L5
VUVG-L18...	18.3	4.5	G1/4	Ø 4.2	M5	43.1	37.8	6.4	129.4	124.4	86.4	112.2	109.7
VUVG-S18...													

Type	L6	L7	L8	L9	L10	L11	L12	L13
VUVG-L18...	86	52	19.7	31.3	23.8	21.7	21.1	14
VUVG-S18...								



## Data sheet

## Dimensions VUVG-...-P1

2x 3/2-way, 5/2-way and 5/3-way valve

Download CAD data → [www.festo.com](http://www.festo.com)

5/2-way valve, single solenoid





[2] Ports 1... 5

Type	B1	D1	D2	H2	H3	L1	L2	L3
VUVG-L18-...-P1	18.3	G1/4	Ø 4.2	43.1	30.6	124.8	86.4	33.9
VUVG-L18-...-P1	52	31.3	23.8	21.1	21.1	22.1	109.9	19




## Ordering data

## ★ Core product range


Ordering data	Description	Part no.	Type	
<b>In-line valve G1/4, with E-box R8</b>				
	<b>2x 3/2-way valve</b>			
	Internal pilot air supply	Normally closed, pneumatic spring reset	★ 8031525	VUVG-L18-T32C-AT-G14-1R8L
	<b>5/2-way single solenoid valve</b>			
	Internal pilot air supply	Pneumatic/mechanical spring reset	★ 8031531	VUVG-L18-M52-RT-G14-1R8L
	Mechanical spring reset	★ 8031532	VUVG-L18-M52-MT-G14-1R8L	
<b>5/3-way valve</b>				
Internal pilot air supply	Mid-position closed, mechanical spring reset	★ 8031534	VUVG-L18-P53CT-G14-1R8L	

Ordering data	Description	Part no.	Type	
<b>In-line valve G1/4, without E-box</b>				
	<b>2x 3/2-way valve</b>			
	Internal pilot air supply	Normally closed, pneumatic spring reset	574422	VUVG-L18-T32C-AT-G14-1P3
		Normally open, pneumatic spring reset	574423	VUVG-L18-T32U-AT-G14-1P3
		1x normally open, 1x normally closed, pneumatic spring reset	574424	VUVG-L18-T32H-AT-G14-1P3
		Normally closed, mechanical spring reset	574425	VUVG-L18-T32C-MT-G14-1P3
		Normally open, mechanical spring reset	574426	VUVG-L18-T32U-MT-G14-1P3
		1x normally open, 1x normally closed, mechanical spring reset	574427	VUVG-L18-T32H-MT-G14-1P3
	External pilot air supply	Normally closed, mechanical spring reset	574434	VUVG-L18-T32C-MZT-G14-1P3
		Normally open, mechanical spring reset	574435	VUVG-L18-T32U-MZT-G14-1P3
		1x normally open, 1x normally closed, mechanical spring reset	574436	VUVG-L18-T32H-MZT-G14-1P3
	<b>5/2-way single solenoid valve</b>			
	Internal pilot air supply	Pneumatic/mechanical spring reset	574428	VUVG-L18-M52-RT-G14-1P3
	Mechanical spring reset	574429	VUVG-L18-M52-MT-G14-1P3	
External pilot air supply	Mechanical spring reset	574438	VUVG-L18-M52-MZT-G14-1P3	
	Pneumatic/mechanical spring reset	574437	VUVG-L18-M52-RZT-G14-1P3	
<b>5/2-way double solenoid valve</b>				
Internal pilot air supply		574430	VUVG-L18-B52-T-G14-1P3	
External pilot air supply		574439	VUVG-L18-B52-ZT-G14-1P3	

## Ordering data

Ordering data		Description	Part no.	Type																																
<b>In-line valve G1/4, without E-box</b>																																				
 <b>5/3-way valve</b> <table border="1"> <tr> <td>Internal pilot air supply</td> <td>Mid-position closed, mechanical spring reset</td> <td>574431</td> <td>VUVG-L18-P53C-T-G14-1P3</td> </tr> <tr> <td></td> <td>Mid-position exhausted, mechanical spring reset</td> <td>574432</td> <td>VUVG-L18-P53E-T-G14-1P3</td> </tr> <tr> <td></td> <td>Mid-position pressurised, mechanical spring reset</td> <td>574433</td> <td>VUVG-L18-P53U-T-G14-1P3</td> </tr> <tr> <td rowspan="3">External pilot air supply</td><td>Mid-position closed, mechanical spring reset</td> <td>574440</td> <td>VUVG-L18-P53C-ZT-G14-1P3</td> </tr> <tr> <td>Mid-position exhausted, mechanical spring reset</td> <td>574441</td> <td>VUVG-L18-P53E-ZT-G14-1P3</td> </tr> <tr> <td>Mid-position pressurised, mechanical spring reset</td> <td>574442</td> <td>VUVG-L18-P53U-ZT-G14-1P3</td> </tr> </table>					Internal pilot air supply	Mid-position closed, mechanical spring reset	574431	VUVG-L18-P53C-T-G14-1P3		Mid-position exhausted, mechanical spring reset	574432	VUVG-L18-P53E-T-G14-1P3		Mid-position pressurised, mechanical spring reset	574433	VUVG-L18-P53U-T-G14-1P3	External pilot air supply	Mid-position closed, mechanical spring reset	574440	VUVG-L18-P53C-ZT-G14-1P3	Mid-position exhausted, mechanical spring reset	574441	VUVG-L18-P53E-ZT-G14-1P3	Mid-position pressurised, mechanical spring reset	574442	VUVG-L18-P53U-ZT-G14-1P3										
Internal pilot air supply	Mid-position closed, mechanical spring reset	574431	VUVG-L18-P53C-T-G14-1P3																																	
	Mid-position exhausted, mechanical spring reset	574432	VUVG-L18-P53E-T-G14-1P3																																	
	Mid-position pressurised, mechanical spring reset	574433	VUVG-L18-P53U-T-G14-1P3																																	
External pilot air supply	Mid-position closed, mechanical spring reset	574440	VUVG-L18-P53C-ZT-G14-1P3																																	
	Mid-position exhausted, mechanical spring reset	574441	VUVG-L18-P53E-ZT-G14-1P3																																	
	Mid-position pressurised, mechanical spring reset	574442	VUVG-L18-P53U-ZT-G14-1P3																																	
<b>In-line valve G1/4, with E-box R8</b>																																				
 <b>2x 3/2-way valve</b> <table border="1"> <tr> <td>Internal pilot air supply</td> <td>Normally open, pneumatic spring reset</td> <td>8031526</td> <td>VUVG-L18-T32U-AT-G14-1R8L</td> </tr> <tr> <td></td> <td>1x normally open, 1x normally closed, pneumatic spring reset</td> <td>8031527</td> <td>VUVG-L18-T32H-AT-G14-1R8L</td> </tr> <tr> <td></td> <td>Normally closed, mechanical spring reset</td> <td>8031528</td> <td>VUVG-L18-T32C-MT-G14-1R8L</td> </tr> <tr> <td></td> <td>Normally open, mechanical spring reset</td> <td>8031529</td> <td>VUVG-L18-T32U-MT-G14-1R8L</td> </tr> <tr> <td></td> <td>1x normally open, 1x normally closed, mechanical spring reset</td> <td>8031530</td> <td>VUVG-L18-T32H-MT-G14-1R8L</td> </tr> </table> <b>5/2-way double solenoid valve</b> <table border="1"> <tr> <td>Internal pilot air supply</td> <td></td> <td>8031533</td> <td>VUVG-L18-B52-T-G14-1R8L</td> </tr> </table> <b>5/3-way valve</b> <table border="1"> <tr> <td>Internal pilot air supply</td> <td>Mid-position exhausted, mechanical spring reset</td> <td>8031535</td> <td>VUVG-L18-P53E-T-G14-1R8L</td> </tr> <tr> <td></td> <td>Mid-position pressurised, mechanical spring reset</td> <td>8031536</td> <td>VUVG-L18-P53U-T-G14-1R8L</td> </tr> </table>					Internal pilot air supply	Normally open, pneumatic spring reset	8031526	VUVG-L18-T32U-AT-G14-1R8L		1x normally open, 1x normally closed, pneumatic spring reset	8031527	VUVG-L18-T32H-AT-G14-1R8L		Normally closed, mechanical spring reset	8031528	VUVG-L18-T32C-MT-G14-1R8L		Normally open, mechanical spring reset	8031529	VUVG-L18-T32U-MT-G14-1R8L		1x normally open, 1x normally closed, mechanical spring reset	8031530	VUVG-L18-T32H-MT-G14-1R8L	Internal pilot air supply		8031533	VUVG-L18-B52-T-G14-1R8L	Internal pilot air supply	Mid-position exhausted, mechanical spring reset	8031535	VUVG-L18-P53E-T-G14-1R8L		Mid-position pressurised, mechanical spring reset	8031536	VUVG-L18-P53U-T-G14-1R8L
Internal pilot air supply	Normally open, pneumatic spring reset	8031526	VUVG-L18-T32U-AT-G14-1R8L																																	
	1x normally open, 1x normally closed, pneumatic spring reset	8031527	VUVG-L18-T32H-AT-G14-1R8L																																	
	Normally closed, mechanical spring reset	8031528	VUVG-L18-T32C-MT-G14-1R8L																																	
	Normally open, mechanical spring reset	8031529	VUVG-L18-T32U-MT-G14-1R8L																																	
	1x normally open, 1x normally closed, mechanical spring reset	8031530	VUVG-L18-T32H-MT-G14-1R8L																																	
Internal pilot air supply		8031533	VUVG-L18-B52-T-G14-1R8L																																	
Internal pilot air supply	Mid-position exhausted, mechanical spring reset	8031535	VUVG-L18-P53E-T-G14-1R8L																																	
	Mid-position pressurised, mechanical spring reset	8031536	VUVG-L18-P53U-T-G14-1R8L																																	
<b>In-line valve G1/4, with E-box H2</b>																																				
 <b>5/2-way single solenoid valve</b> <table border="1"> <tr> <td>Internal pilot air supply</td> <td>Pneumatic/mechanical spring reset</td> <td>578823</td> <td>VUVG-L18-M52-RT-G14-1H2L-W1</td> </tr> </table>					Internal pilot air supply	Pneumatic/mechanical spring reset	578823	VUVG-L18-M52-RT-G14-1H2L-W1																												
Internal pilot air supply	Pneumatic/mechanical spring reset	578823	VUVG-L18-M52-RT-G14-1H2L-W1																																	

## Ordering data

Ordering data		Description	Part no.	Type
<b>In-line valve G1/4, to ISO 15218</b>				
	<b>2x 3/2-way valve</b>	Internal pilot air supply	8033547	VUVG-L18-T32C-A-G14-P1
		Normally closed, pneumatic spring reset	8033548	VUVG-L18-T32U-A-G14-P1
		Normally open, pneumatic spring reset	8033549	VUVG-L18-T32H-A-G14-P1
		1x normally open, 1x normally closed, pneumatic spring reset	8033550	VUVG-L18-T32C-M-G14-P1
		1x normally closed, 1x normally open, pneumatic spring reset	8033551	VUVG-L18-T32U-M-G14-P1
		1x normally open, 1x normally closed, mechanical spring reset	8033552	VUVG-L18-T32H-M-G14-P1
<b>5/2-way valve, single solenoid</b>				
Internal pilot air supply	Pneumatic/mechanical spring reset	8033553	VUVG-L18-M52-R-G14-P1	
	Mechanical spring reset	8033554	VUVG-L18-M52-M-G14-P1	
<b>5/2-way, valve, double solenoid</b>				
Internal pilot air supply		8033555	VUVG-L18-B52-G14-P1	
<b>5/3-way valve</b>				
Internal pilot air supply	Mid-position closed, mechanical spring reset	8033556	VUVG-L18-P53C-G14-P1	
	Mid-position exhausted, mechanical spring reset	8033557	VUVG-L18-P53E-G14-P1	
	Mid-position pressurised, mechanical spring reset	8033558	VUVG-L18-P53U-G14-P1	



## Manifold assembly

In-line valves for  
manifold assembly



### Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



Note

Additional dimensions  
E-boxes  
→ Page 104


- |   |  |  |   |
|---|--|--|---|
| [1] Ports 1, 3 and 5: G3/8 (at both ends)             | [6] H-rail mounting (two M4x35 screws are required for mounting) | [7] Cover plate                          | [9] Valves/cover plate mounting on manifold rail: M3 thread |
| [2] Ports 2 and 4: G1/4                               |  | [8] Supply plate, ports 1, 3 and 5: G1/4 |   |
| [5] Electrical connection for E-boxes and accessories |  |  |   |

Type	B1	B2	B3	B4	B5	B6	B7	B8	B9	D1
VABM-L1-18S-G38	129.4	124.4	95.6	76.8	47.8	18.8	51.7	34.8	26	4.5

Type	H1	H2	H3	H4	H5	H6	L3	L4	L5	L6
VABM-L1-18S-G38	72.1	29	11.5	28.4	27.6	6.5	6	20.5	19	1

Valve positions	2	3	4	5	6	7	8	9	10	12	14	16
L1	61	80	99	118	137	156	175	194	213	251	289	327
L2	49	68	87	106	125	144	163	182	201	239	277	315
VABM weight [g]	118	159	200	241	282	323	364	405	446	528	610	692


## Ordering data

Technical data – Manifold rails		Connection	CRC	Material <sup>2)</sup>	Operating pressure		Max. tightening torque for assembly [Nm]		
		1, 3, 5			[MPa]	[bar]	Valve	H-rail	Wall
	G3/8	2 <sup>1)</sup>	Wrought aluminium alloy		-0.09 ... 1	-0.9 ... 10	1.18	1.5	3



1) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

2) Note on materials: RoHS-compliant.

Ordering data – Manifold rail		Description	Part no.	Type
<b>Manifold rail for in-line valve</b>				
	For size G1/4	2 valve positions	 <a href="#">574455</a>	VABM-L1-18S-G38-2
		3 valve positions	 <a href="#">574456</a>	VABM-L1-18S-G38-3
		4 valve positions	 <a href="#">574457</a>	VABM-L1-18S-G38-4
		5 valve positions	<a href="#">574458</a>	VABM-L1-18S-G38-5
		6 valve positions	 <a href="#">574459</a>	VABM-L1-18S-G38-6
		7 valve positions	<a href="#">574460</a>	VABM-L1-18S-G38-7
		8 valve positions	 <a href="#">574461</a>	VABM-L1-18S-G38-8
		9 valve positions	<a href="#">574462</a>	VABM-L1-18S-G38-9
		10 valve positions	 <a href="#">574463</a>	VABM-L1-18S-G38-10
		12 valve positions	<a href="#">574464</a>	VABM-L1-18S-G38-12
		14 valve positions	<a href="#">574465</a>	VABM-L1-18S-G38-14
		16 valve positions	<a href="#">574466</a>	VABM-L1-18S-G38-16

## Ordering data

Ordering data – Accessories		Description	Part no.	Type
Cover plate				Data sheets → Internet: vabb
	For valve position on manifold rail, including screws and seal	★ 574482	VABB-L1-18	
Separator				Data sheets → Internet: vabd
	For creating pressure zones	574483	VABD-14-B	
Supply plate				Data sheets → Internet: vabf
	For valve position on manifold rail, including screws and seal	574481	VABF-L1-18-P3A4-G14	
Seals for in-line valves				Data sheets → Internet: vabd
	For G1/4 in-line valves	Delivery quantity: 10 sets (each with 2 screws and 1 seal)	★ 574479	VABD-L1-18X-S-G14



**Note**  
Connect supply plate at port 1 with compressed air. Reverse operation (pressure at port 3, 5) is not permissible.

# Solenoid valves VUVG-B10A, sub-base valves M3

## Data sheet

### Function

5/2-way, single solenoid

-  - Size 10 mm

5/2-way, double solenoid valve

-  - Flow rate  
90 ... 100 l/min

5/3C, 5/3U, 5/3E

-  - Voltage  
5, 12 and 24 V DC

Circuit symbols → page 13



### General technical data VUVG-B

Valve function	M52-R	B52	M52-M	P53		
Normal position	-	-	-	C <sup>1)</sup>	U <sup>2)</sup>	E <sup>3)</sup>
Stable position	Monostable	Bistable	Monostable	Monostable		
Pneumatic spring reset	Yes <sup>4)</sup>	-	No	-		
Mechanical spring reset	Yes <sup>4)</sup>	-	Yes	Yes		
Vacuum operation at port 1	Only with external pilot air supply					
Design	Piston spool					
Sealing principle	Soft					
Type of actuation	Electrical					
Type of control	Piloted					
Pilot air supply	External, internal; can be selected via sub-base					
Exhaust function	Can be throttled					
Manual override	Choice of non-detenting, covered, non-detenting/detenting or detenting					
Type of mounting	On manifold rail					
Mounting position	Any					
Nominal width	[mm]	2	1.4	2		
Standard nominal flow rate	[l/min]	100	80	90		
Flow rate on manifold rail M3	[l/min]	100	80	90		
Switching time on/off	[ms]	7/15	-	7/21	8/25	
Switching time changeover	[ms]	-	5	-	14	
Size	[mm]	10				
Connection	1, 3, 5 2, 4 12/14, 82/84	M7 in manifold rail M5 in manifold rail M5 in manifold rail				
Product weight	[g]	38	49	37	49	
Certification	c UL us - Recognized (OL) RCM compliance mark					
CE marking (see declaration of conformity) <sup>5)</sup>	To EU EMC Directive					
Corrosion resistance class CRC <sup>6)</sup>	2					

1) C=Normally closed/mid-position closed

2) U=Normally open/mid-position pressurised

3) E=Mid-position exhausted

4) Combined reset method

5) For information about the area of use, see the EC declaration of conformity at: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/) → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

6) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

## Data sheet

Operating and environmental conditions		M52-R <sup>1)</sup>	B52	M52-M <sup>2)</sup>	P53
Valve function					
Operating medium	Compressed air to ISO 8573-2010 [7:4:4]				
	Internal	[MPa]	0.25 ... 0.8	0.15 ... 0.8	0.3 ... 0.8
		[bar]	2.5 ... 8	1.5 ... 8	3 ... 8
	External	[MPa]	-0.09 ... 1	-0.09 ... 0.8	-0.09 ... 1
		[bar]	-0.9 ... 10	-0.9 ... 8	-0.9 ... 10
Pilot pressure	[MPa]	0.25 ... 0.8	0.15 ... 0.8	0.3 ... 0.8	
	[bar]	2.5 ... 8	1.5 ... 8	3 ... 8	
Ambient temperature	[°C]	-5 ... +50, with holding current reduction -5 ... +60			
Temperature of medium	[°C]	-5 ... +50, with holding current reduction -5 ... +60			

1) Mixed, pneumatic/mechanical spring

2) Mechanical spring

### Electrical data

Electrical connection	Via E-box → page 102
Operating voltage	[V DC] 5, 12 and 24 ±10%
Power	[W] 1, reduced to 0.35 with holding current reduction
Duty cycle	[%) 100
Degree of protection to EN 60529	IP40 (with plug socket), IP65 (with M8)


### Information on materials

Housing	Wrought aluminium alloy
Seals	HNBR, NBR
Note on materials	RoHS-compliant

### Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

5/2-way and 5/3-way valve




- - Note  
Additional dimensions  
E-boxes  
→ Page 104

[1] Vertical electrical connection

[2] Manual override

Type	B1	H1	L1	L2	L3	L4	L5	L6	L7
VUVG-B10A-...-F...	10.2	32.5	73.9	68.9	8	4.85	6.15	56.9	54.4

## Ordering data

Ordering data	Description	Part no.	Type
<b>Sub-base valve M3, without E-box</b>			
<b>5/2-way single solenoid valve</b>			
	External pilot air supply	Pneumatic/mechanical spring reset	566448 VUVG-B10A-M52-RZT-F-1P3
		Mechanical spring reset	574347 VUVG-B10A-M52-MZT-F-1P3
<b>5/2-way double solenoid valve</b>			
External pilot air supply		566449	VUVG-B10A-B52-ZT-F-1P3
<b>5/3-way valve</b>			
External pilot air supply	Mid-position closed, mechanical spring reset	566450	VUVG-B10A-P53C-ZT-F-1P3
	Mid-position exhausted, mechanical spring reset	566451	VUVG-B10A-P53E-ZT-F-1P3
	Mid-position pressurised, mechanical spring reset	566452	VUVG-B10A-P53U-ZT-F-1P3

## Manifold assembly

**Sub-base valve for  
manifold assembly**  
**Connection M5**



### Dimensions


Download CAD data → [www.festo.com](http://www.festo.com)

- - Note

Additional dimensions

E-boxes

→ Page 104



[1] Ports 1, 3 and 5: M7 (at both ends)

[2] Ports 2, 4: M5

[3] Ports 12, 14: M5

[4] Ports 82, 84: M5

[5] Electrical connection for E-boxes and accessories

[6] H-rail mounting (two M4x25 screws are required for mounting)

[7] Cover plate

[8] Supply plate, ports 1, 3 and 5: M5

[9] Valves/cover plate mounting on manifold rail: M2 thread


Type	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12
VABM-L1-10AW-M7	84.9	62.4	39.1	35	29.8	17.8	8.2	24	7.2	43.5	45.8	39.2

Type	D1	D2	D3	D4	D5	H1	H2	H3	H4	H5	H6
VABM-L1-10AW-M7	M7	M5	M5	Ø 4.5	Ø 4	53.1	12	9.1	6.3	11.6	3.6

Type	H7	H8	H9	H10	H15	L3	L5	L6	L7	L8	L9	L10	L11
VABM-L1-10AW-M7	13.1	4.2	16.2	6.8	1.9	7.5	12.5	10.5	10.2	10.5	17	15.2	14

Valve positions	2	3	4	5	6	7	8	9	10	12	14	16
L1	43.5	54	64.5	75	85.5	97	107.5	117	127.5	148.5	169.5	190.5
L2	28.5	39	49.5	60	70.5	81	91.5	102	112.5	133.5	154.5	175.5
L4	36.5	47	57.5	68	78.5	89	99.5	110	120.5	141.5	162.5	183.5
VABM weight [g]	60	78	96	114	132	150	168	186	204	240	276	312

## Ordering data


Technical data – Manifold rails <sup>1)</sup>				CRC	Material <sup>3)</sup>	Operating pressure		Max. tightening torque for assembly [Nm]		
Connection	2, 4	1, 3, 5	12/14, 82/84		[MPa]	[bar]	Valve	H-rail	Wall	
	M5	M7	M5	2 <sup>2)</sup>	Wrought aluminium alloy	-0.09 ... 1	-0.9 ... 10	0.45	1.5	1.5



1) Blanking plugs are included with the manifold rail.

2) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

3) Note on materials: RoHS-compliant.


Ordering data – Manifold rails		Description	Part no.	Type
<b>Manifold rail for sub-base valve M3</b>				
	For size B10A (M3)	2 valve positions	566546	VABM-L1-10AW-M7-2
		3 valve positions	566547	VABM-L1-10AW-M7-3
		4 valve positions	566548	VABM-L1-10AW-M7-4
		5 valve positions	566549	VABM-L1-10AW-M7-5
		6 valve positions	566550	VABM-L1-10AW-M7-6
		7 valve positions	566551	VABM-L1-10AW-M7-7
		8 valve positions	566552	VABM-L1-10AW-M7-8
		9 valve positions	566553	VABM-L1-10AW-M7-9
		10 valve positions	566554	VABM-L1-10AW-M7-10
		12 valve positions	566555	VABM-L1-10AW-M7-12
		14 valve positions	566556	VABM-L1-10AW-M7-14
		16 valve positions	566557	VABM-L1-10AW-M7-16

Ordering data – Accessories		Description	Part no.	Type
Cover plate				Data sheets → Internet: vabb
	For valve position on manifold rail, including screws and seal		569986	VABB-L1-10A
Separator				Data sheets → Internet: vabd
	For creating pressure zones		570872	VABD-4.2-B
Supply plate				Data sheets → Internet: vabf
	For valve position on manifold rail, including screws and seal		569990	VABF-L1-10A-P3A4-M5
Seals				Data sheets → Internet: vabd
	For sub-base valve M3	Delivery quantity: 10 sets (each with 2 screws and 1 seal)	566671	VABD-L1-10AB-S-M3

## Data sheet

Function  
2x 3/2C  
5/2-way, single solenoid  
5/2-way, double solenoid valve  
  
Circuit symbols → page 13

- - Size 10 mm
- - Flow rate  
160 l/min
- - Voltage  
24 V DC



### General technical data VUVG-BK

Valve function	T32-A	M52-A	B52
Normal position	C <sup>1)</sup>	-	-
Stable position	Monostable		Bistable
Pneumatic spring reset	Yes	Yes	-
Design	Piston spool		
Sealing principle	Soft		
Type of actuation	Electrical		
Type of control	Piloted		
Pilot air supply	Internal		
Exhaust function	Can be throttled		
Manual override	Non-detenting, detenting		
Type of mounting	On manifold rail		
Mounting position	Any		
Standard nominal flow rate	[l/min]	160	160
Switching time on/off	[ms]	12/14	14/17
Switching time changeover	[ms]	-	7
Size	[mm]	10	
Connection	2, 4	M5/M7 in manifold rail	
Product weight	[g]	55	45
Corrosion resistance class CRC <sup>2)</sup>		2	57

1) C=Normally closed

2) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

### Safety data

Max. positive test pulse with 0 signal	[μs]	1600
Max. negative test pulse with 1 signal	[μs]	3000
Shock resistance		Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27
Vibration resistance		Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6


## Data sheet

Operating and environmental conditions			
Valve function	T32-A <sup>1)</sup>	M52-A <sup>1)</sup>	B52
Operating medium	Compressed air to ISO 8573-2010 [7:4:4]		
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)		
Operating pressure	[MPa]	0.15 ... 0.7	0.25 ... 0.7
	[bar]	1.5 ... 7	2.5 ... 7
Ambient temperature	[°C]	-5 ... +50	
Temperature of medium	[°C]	-5 ... +50	


1) Pneumatic spring

Electrical data					
Electrical connection	Via E-box → page 102				
Operating voltage	[V DC]	24 ±10%			
Nominal operating voltage	[V DC]	22			
Power	[W]	0.7			
Duty cycle	[%]	100			
Degree of protection to EN 60529	IP40 (with plug socket), IP65 (with M8)				
Signal status display	LED				
Maximum switching frequency	[Hz]	2			

Information on materials			
Housing	Wrought aluminium alloy		
Seals	HNBR, NBR		
Note on materials	RoHS-compliant Contains paint-wetting impairment substances		

Pin allocation for E-box			
	Pin		Description
Rectangular plug, connection pattern H			
	1	+ or -	Protective circuit without holding current reduction
	2	+ or -	
Round plug, M8, 3-pin			
	1	Not used	Protective circuit without holding current reduction
	3	+ or -	
	4	+ or -	

## Protective circuit without holding current reduction




The solenoid coils have a protective circuit to arrest sparks and protect against polarity reversal.


## Data sheet

### Dimensions

2x 3/2-way, 5/2-way valve, double solenoid

Download CAD data → [www.festo.com](http://www.festo.com)

5/2-way single solenoid valve



**Note**

Additional dimensions

E-boxes

→ Page 104

[2] Horizontal electrical connection

[3] Manual override

Type	B1	H1	L1	L2	L7
VUVG-BK10-T32C...	10.2	33.6	98.3	95.8	47
VUVG-BK10-B52...			75.9	74.6	
VUVG-BK10-M52...					

## Ordering data

### ★ Core product range

#### Ordering data

	Description		Part no.	Type
<b>Sub-base valve M5/M7, with E-box R8</b>				
	<b>2x 3/2-way valve</b>			
	Internal pilot air supply	Normally closed, pneumatic spring reset	★ 8042558	VUVG-BK10-T32C-AT-F-1R8L-S
	<b>5/2-way single solenoid valve</b>			
	Internal pilot air supply	Pneumatic spring reset	★ 8042559	VUVG-BK10-M52-AT-F-1R8L-S
	<b>5/2-way double solenoid valve</b>			
	Internal pilot air supply		★ 8042560	VUVG-BK10-B52-T-F-1R8L-S
<b>Sub-base valve M5/M7, with E-box H2</b>				
	<b>2x 3/2-way valve</b>			
	Internal pilot air supply	Normally closed, pneumatic spring reset	★ 8042554	VUVG-BK10-T32C-AT-F-1H2L-S
	<b>5/2-way single solenoid valve</b>			
	Internal pilot air supply	Pneumatic spring reset	★ 8042555	VUVG-BK10-M52-AT-F-1H2L-S
	<b>5/2-way double solenoid valve</b>			
	Internal pilot air supply		★ 8042556	VUVG-BK10-B52-T-F-1H2L-S

## Data sheet

### Function

2x 3/2C, 2x 3/2U, 2x 3/2H

5/2-way, single solenoid

5/2-way, double solenoid valve

5/3C, 5/3U, 5/3E

- - Size 10 mm

- - Flow rate  
120 ... 270 l/min

- - Voltage  
5, 12 and 24 V DC

Circuit symbols → page 13



### General technical data VUVG-B

Valve function	T32-A	T32-M			M52-R	B52	M52-M	P53																
	C <sup>1)</sup>	U <sup>2)</sup>	H <sup>4)</sup>	C <sup>1)</sup>	U <sup>2)</sup>	H <sup>4)</sup>	-	C <sup>1)</sup>	U <sup>2)</sup>	E <sup>3)</sup>														
Normal position							-	-	-															
Stable position	Monostable						Bistable	Monostable	Monostable															
Pneumatic spring reset	Yes	No		Yes <sup>5)</sup>		-	No	-																
Mechanical spring reset	No	Yes		Yes <sup>5)</sup>		-	Yes	Yes																
Vacuum operation at port 1	No	Only with external pilot air supply																						
Design	Piston spool																							
Sealing principle	Soft																							
Type of actuation	Electrical																							
Type of control	Piloted																							
Pilot air supply	External, internal; can be selected via sub-base																							
Exhaust function	Can be throttled																							
Manual override	Choice of non-detenting, covered, non-detenting/detenting or detenting																							
Type of mounting	On manifold rail																							
Mounting position	Any																							
Nominal width	[mm]	2.7	1.8	1.7	4				2.3	3.5														
Standard nominal flow rate	[l/min]	170	150	140	140	330				285														
Flow rate on manifold rail M5	[l/min]	150	130	120	120	210				200														
Flow rate on manifold rail M7	[l/min]	160	140	130	130	270				250														
Switching time on/off	[ms]	6/15	8/11			7/17	-	8/24	11/30															
Switching time changeover	[ms]	-				7				14														
Size	[mm]	10																						
Connection	1, 3, 5	G1/8 in manifold rail																						
	2, 4	M5 or M7 in manifold rail																						
	12/14, 82/84	M5 in manifold rail																						
Product weight	[g]	55	54	45		55	44	55																
Certification	c UL us - Recognized (OL) RCM compliance mark																							
CE marking (see declaration of conformity) <sup>6)</sup>	To EU EMC Directive																							
Corrosion resistance class CRC <sup>7)</sup>	2																							

1) C=Normally closed/mid-position closed

2) U=Normally open/mid-position pressurised

3) E=Mid-position exhausted

4) H=2x 3/2-way valve in one housing with 1x normally closed and 1x normally open

5) Combined reset method

6) For information about the area of use, see the EC declaration of conformity at: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/) → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

7) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

## Data sheet

Operating and environmental conditions		T32-A <sup>1)</sup>	T32-M <sup>3)</sup>	M52-R <sup>2)</sup>	B52	M52-M <sup>3)</sup>	P53
Valve function							
Operating medium	Compressed air to ISO 8573-2010 [7:4:4]						
Operating pressure	Internal	[MPa]	0.15 ... 0.8	0.25 ... 0.8	0.25 ... 0.8	0.15 ... 0.8	0.3 ... 0.8
		[bar]	1.5 ... 8	2.5 ... 8	2.5 ... 8	1.5 ... 8	3 ... 8
Pilot pressure	External	[MPa]	0.15 ... 1	-0.09 ... 1		-0.09 ... 0.8	-0.09 ... 1
		[bar]	1.5 ... 10	-0.9 ... 10		-0.9 ... 8	-0.9 ... 10
Ambient temperature	[°C]	0.15 ... 0.8	0.2 ... 0.8	0.25 ... 0.8	0.15 ... 0.8	0.3 ... 0.8	
Temperature of medium	[°C]	1.5 ... 8	2 ... 8	2.5 ... 8	1.5 ... 8	3 ... 8	

1) Pneumatic spring

2) Mixed, pneumatic/mechanical spring

3) Mechanical spring

### Electrical data

Electrical connection	Via E-box → page 102
Operating voltage	[V DC] 5, 12 and 24 ±10%
Power	[W] 1, reduced to 0.35 with holding current reduction
Duty cycle	[%] 100
Degree of protection to EN 60529	IP40 (with plug socket), IP65 (with M8)


### Information on materials

Housing	Wrought aluminium alloy
Seals	HNBR, NBR
Note on materials	RoHS-compliant

### Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

2x 3/2-way, 5/2-way and 5/3-way valve



- Note  
 Additional dimensions  
 E-boxes  
 → Page 104



[1] Vertical electrical connection

[2] Horizontal electrical connection

[3] Manual override

Type	B1	H1	H2	L1	L2	L3	L4	L5	L6	L7
VUVG-B10-...-F...	10.2	32.5	3.6	86.5	81.5	8	4.85	6.15	69.2	66.7

## Ordering data

Ordering data		Description	Part no.	Type	
<b>Sub-base valve M5/M7, without E-box</b>					
	<b>2x 3/2-way valve</b>				
	External pilot air supply	Normally closed, pneumatic spring reset	566487	VUVG-B10-T32C-AZT-F-1P3	
		Normally open, pneumatic spring reset	566488	VUVG-B10-T32U-AZT-F-1P3	
		1x normally open, 1x normally closed, pneumatic spring reset	566489	VUVG-B10-T32H-AZT-F-1P3	
		Normally closed, mechanical spring reset	574364	VUVG-B10-T32C-MZT-F-1P3	
		Normally open, mechanical spring reset	574365	VUVG-B10-T32U-MZT-F-1P3	
		<b>5/2-way single solenoid valve</b>	1x normally open, 1x normally closed, mechanical spring reset	574366	VUVG-B10-T32H-MZT-F-1P3
	External pilot air supply		Pneumatic/mechanical spring reset	566490	VUVG-B10-M52-RZT-F-1P3
			Mechanical spring reset	574367	VUVG-B10-M52-MZT-F-1P3
	<b>5/2-way double solenoid valve</b>				
	External pilot air supply			566491	VUVG-B10-B52-ZT-F-1P3
	<b>5/3-way valve</b>				
External pilot air supply	Mid-position closed, mechanical spring reset	566492	VUVG-B10-P53C-ZT-F-1P3		
	Mid-position exhausted, mechanical spring reset	566493	VUVG-B10-P53E-ZT-F-1P3		
	Mid-position pressurised, mechanical spring reset	566494	VUVG-B10-P53U-ZT-F-1P3		
<b>Sub-base valve M5/M7, with E-box R8</b>					
	<b>2x 3/2-way valve</b>				
	External pilot air supply	Normally closed, pneumatic spring reset	574234	VUVG-B10-T32C-AZT-F-1R8L	
		Normally open, pneumatic spring reset	574235	VUVG-B10-T32U-AZT-F-1R8L	
		1x normally open, 1x normally closed, pneumatic spring reset	574236	VUVG-B10-T32H-AZT-F-1R8L	
		Normally closed, mechanical spring reset	8031492	VUVG-B10-T32C-MZT-F-1R8L	
		Normally open, mechanical spring reset	8031493	VUVG-B10-T32U-MZT-F-1R8L	
		<b>5/2-way single solenoid valve</b>	1x normally open, 1x normally closed, mechanical spring reset	8031494	VUVG-B10-T32H-MZT-F-1R8L
	External pilot air supply		Pneumatic/mechanical spring reset	574237	VUVG-B10-M52-RZT-F-1R8L
			Mechanical spring reset	578157	VUVG-B10-M52-MZT-F-1R8L
	<b>5/2-way double solenoid valve</b>				
	External pilot air supply			574238	VUVG-B10-B52-ZT-F-1R8L
	<b>5/3-way valve</b>				
External pilot air supply	Mid-position closed, mechanical spring reset	574239	VUVG-B10-P53C-ZT-F-1R8L		
	Mid-position exhausted, mechanical spring reset	574241	VUVG-B10-P53E-ZT-F-1R8L		
	Mid-position pressurised, mechanical spring reset	574240	VUVG-B10-P53U-ZT-F-1R8L		

## Manifold assembly

**Sub-base valve for  
manifold assembly**  
M5 or M7 connection



### Dimensions



Download CAD data → [www.festo.com](http://www.festo.com)

- - Note

Additional dimensions

E-boxes

→ Page 104



[1] Ports 1, 3 and 5: G1/8 (at both ends)

[2] Ports 2, 4:  
M7 or M5

[3] Ports 12, 14: M5

[5] Electrical connection for E-boxes and accessories

[6] H-rail mounting (two M4x30 screws are required for mounting)


[7] Cover plate

[8] Supply plate,  
ports 1, 3 and 5:  
either M5 or M7

[9] Valves/cover plate mounting on manifold rail: M2 thread

Type	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12
VABM-L1 10-...-G18	97.5	74.8	52.9	46.5	40.9	24.9	8.9	61.7	57.7	16.9	16	42.2
Type	B13	B14	D1	D2	D3	D4	D5	H1	H2	H3	H4	
VABM-L1 10-...-G18	39.3	14.1	G1/8	M5/M7	M5	4.5	Ø 6	56.4	15.7	12.2	7.9	
Type	H5	H6	H7	H8	H9	H10	H11	L3	L4	L5	L6	L7
VABM-L1 10-...-G18	23.9	10.8	4	17.6	5.9	18	6.8	6	10.5	10.3	16	11.9
Valve positions	2	3	4	5	6	7	8	9	10	12	14	16
L1	40.5	51	61.5	72	82.5	93	103.5	114	124.5	145.5	166.5	187.5
L2	30.5	41	51.5	62	72.5	83	93.5	104	114.5	135.5	156.5	177.5
VABM weight [g]	107	135	163	191	219	247	275	303	331	387	415	471
												499

## Manifold assembly


Technical data – Manifold rails <sup>1)</sup>			CRC	Material <sup>3)</sup>	Operating pressure		Max. tightening torque for assembly [Nm]			
Connection	2, 4	1, 3, 5	12/14, 82/84		[MPa]	[bar]	Valve	H-rail	Wall	
	M5 or M7	G1/8	M5	2 <sup>2)</sup>	Wrought aluminium alloy	-0.09 ... 1	-0.9 ... 10	0.45	1.5	3

1) Blanking plugs are included with the manifold rail.




2) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

3) Note on materials: RoHS-compliant.


Ordering data – Manifold rails		Description	Part no.	Type
<b>Manifold rail for sub-base valve M5/M7</b>				
	For size B10 (M5)	2 valve positions	 <a href="#">566582</a>	VABM-L1-10W-G18-2
		3 valve positions	 <a href="#">566583</a>	VABM-L1-10W-G18-3
		4 valve positions	 <a href="#">566584</a>	VABM-L1-10W-G18-4
		5 valve positions	<a href="#">566585</a>	VABM-L1-10W-G18-5
		6 valve positions	 <a href="#">566586</a>	VABM-L1-10W-G18-6
		7 valve positions	<a href="#">566587</a>	VABM-L1-10W-G18-7
		8 valve positions	 <a href="#">566588</a>	VABM-L1-10W-G18-8
		9 valve positions	<a href="#">566589</a>	VABM-L1-10W-G18-9
		10 valve positions	 <a href="#">566590</a>	VABM-L1-10W-G18-10
		12 valve positions	<a href="#">566591</a>	VABM-L1-10W-G18-12
		14 valve positions	<a href="#">566592</a>	VABM-L1-10W-G18-14
		16 valve positions	<a href="#">566593</a>	VABM-L1-10W-G18-16

## Manifold assembly

Ordering data – Accessories		Description	Part no.	Type
<b>Manifold rail for sub-base valve M5/M7</b>				
	For size B10 (M7)	2 valve positions 3 valve positions 4 valve positions 5 valve positions 6 valve positions 7 valve positions 8 valve positions 9 valve positions 10 valve positions 12 valve positions 14 valve positions 16 valve positions	★ 566606 ★ 566607 ★ 566608 566609 ★ 566610 566611 ★ 566612 566613 ★ 566614 566615 566616 566617	VABM-L1-10HW-G18-2 VABM-L1-10HW-G18-3 VABM-L1-10HW-G18-4 VABM-L1-10HW-G18-5 VABM-L1-10HW-G18-6 VABM-L1-10HW-G18-7 VABM-L1-10HW-G18-8 VABM-L1-10HW-G18-9 VABM-L1-10HW-G18-10 VABM-L1-10HW-G18-12 VABM-L1-10HW-G18-14 VABM-L1-10HW-G18-16
Cover plate				Data sheets → Internet: vabb
	For valve position on manifold rail, including screws and seal		★ 566495	VABB-L1-10-W
Separator				Data sheets → Internet: vabd
	For creating pressure zones		569994	VABD-6-B
Supply plate				Data sheets → Internet: vabf
	For valve position (sub-base valves M5) on manifold rail, including screws and seal For valve position (sub-base valves M7) on manifold rail, including screws and seal		569991 569992	VABF-L1-10-P3A4-M5 VABF-L1-10-P3A4-M7
Seals				Data sheets → Internet: vabd
	For sub-base valves M5/M7	Delivery quantity: 10 sets (each with 2 screws and 1 seal)	566674	VABD-L1-10B-S-M7

## Data sheet

Function 2x 3/2C	-  - Size 14 mm
5/2-way, single solenoid	-  - Flow rate 350 ... 380 l/min
5/2-way, double solenoid valve	-  - Voltage 24 V DC
Circuit symbols → page 13	



## General technical data VUVG-BK

Valve function	T32-A	M52-A	B52
Normal position	C <sup>1)</sup>	-	-
Stable position	Monostable		Bistable
Pneumatic spring reset	Yes	Yes	-
Design	Piston spool		
Sealing principle	Soft		
Type of actuation	Electrical		
Type of control	Piloted		
Pilot air supply	Internal		
Exhaust function	Can be throttled		
Manual override	Non-detenting, detenting		
Type of mounting	On manifold rail		
Mounting position	Any		
Standard nominal flow rate	[l/min]	350	380
Switching time on/off	[ms]	13/20	14/24
Switching time changeover	[ms]	-	8
Size	[mm]	14	
Connection	2, 4	G1/8 in manifold rail	
Product weight	[g]	75	65
Corrosion resistance class CRC <sup>2)</sup>		2	85

1) C=Normally closed

2) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

## Safety data

Max. positive test pulse with 0 signal	[μs]	1600
Max. negative test pulse with 1 signal	[μs]	3000
Shock resistance		Shock test with severity level 1 to FN 942017-5 and EN 60068-2-27
Vibration resistance		Transport application test with severity level 1 to FN 942017-4 and EN 60068-2-6



## Data sheet

Operating and environmental conditions			
Valve function	T32-A <sup>1)</sup>	M52-A <sup>1)</sup>	B52
Operating medium	Compressed air to ISO 8573-2010 [7:4:4]		
Note on the operating/pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)		
Operating pressure	[MPa]	0.15 ... 0.7	0.25 ... 0.7
	[bar]	1.5 ... 7	2.5 ... 7
Ambient temperature	[°C]	-5 ... +50	1.5 ... 7
Temperature of medium	[°C]	-5 ... +50	


1) Pneumatic spring

Electrical data			
Electrical connection	Via E-box → page 102		
Operating voltage	[V DC] 24 ±10%		
Nominal operating voltage	[V DC] 22		
Power	[W] 0.7		
Duty cycle	[%] 100		
Degree of protection to EN 60529	IP40 (with plug socket), IP65 (with M8)		
Signal status display	LED		
Maximum switching frequency	[Hz]	2	

Information on materials			
Housing	Wrought aluminium alloy		
Seals	HNBR, NBR		
Note on materials	RoHS-compliant Contains paint-wetting impairment substances		

Pin allocation for E-box			
	Pin	Description	
Rectangular plug, connection pattern H			
	1	+ or -	Protective circuit without holding current reduction
	2	+ or -	
Round plug, M8, 3-pin			
	1	Not used	Protective circuit without holding current reduction
	3	+ or -	
	4	+ or -	

### Protective circuit without holding current reduction



The solenoid coils have a protective circuit to arrest sparks and protect against polarity reversal.



## Data sheet

### Dimensions

2x 3/2-way, 5/2-way valve, single solenoid

5/2-way double solenoid valve

Download CAD data → [www.festo.com](http://www.festo.com)



#### Note

Additional dimensions

E-boxes

→ Page 104

[2] Horizontal electrical connection

[3] Manual override

Type	B1	H1	L1	L2	L7
VUVG-BK14-T32C...	14.4	34.8	118.9	116.4	66.5
VUVG-BK14-B52...			95.6	94.4	
VUVG-BK14-M52...					

## Ordering data

### ★ Core product range

Ordering data	Description	Part no.	Type
<b>Sub-base valve G1/8, with E-box R8</b>			
	<b>2x 3/2-way valve</b> Internal pilot air supply      Normally closed, pneumatic spring reset	★ 8042574	VUVG-BK14-T32C-AT-F-1R8L-S
	<b>5/2-way single solenoid valve</b> Internal pilot air supply      Pneumatic spring reset	★ 8042575	VUVG-BK14-M52-AT-F-1R8L-S
	<b>5/2-way double solenoid valve</b> Internal pilot air supply	★ 8042576	VUVG-BK14-B52-T-F-1R8L-S
<b>Sub-base valve G1/8, with E-box H2</b>			
	<b>2x 3/2-way valve</b> Internal pilot air supply      Normally closed, pneumatic spring reset	★ 8042570	VUVG-BK14-T32C-AT-F-1H2L-S
	<b>5/2-way single solenoid valve</b> Internal pilot air supply      Pneumatic spring reset	★ 8042571	VUVG-BK14-M52-AT-F-1H2L-S
	<b>5/2-way double solenoid valve</b> Internal pilot air supply	★ 8042572	VUVG-BK14-B52-T-F-1H2L-S

## Data sheet

### Function

2x 3/2C, 2x 3/2U, 2x 3/2H

- - Size 14 mm

5/2-way, single solenoid


- - Flow rate  
410 ... 700 l/min

5/2-way, double solenoid valve

- - Voltage  
5, 12 and 24 V DC

5/3C, 5/3U, 5/3E

Circuit symbols → page 13



### General technical data VUVG-B

Valve function	T32-A	T32-M			M52-A	B52	M52-M	P53											
	C <sup>1)</sup>	U <sup>2)</sup>	H <sup>4)</sup>	C <sup>1)</sup>	U <sup>2)</sup>	H <sup>4)</sup>	-	C <sup>1)</sup>	U <sup>2)</sup>	E <sup>3)</sup>									
Normal position							-	-	-	C <sup>1)</sup>									
Stable position	Monostable			Bistable			Monostable	Monostable											
Pneumatic spring reset	Yes	No			Yes	-	No	-											
Mechanical spring reset	No	Yes			No	-	Yes	Yes											
Vacuum operation at port 1	No	Only with external pilot air supply																	
Size	[mm]	14																	
Design	Piston spool																		
Sealing principle	Soft																		
Type of actuation	Electrical																		
Type of control	Piloted																		
Pilot air supply	External, internal; can be selected via sub-base																		
Exhaust function	Can be throttled																		
Manual override	VUVG...	Choice of non-detenting, covered, non-detenting/detenting or detenting																	
	VUVG-...-P1	Non-detenting, non-detenting/detenting																	
Type of mounting	On manifold rail																		
Mounting position	Any																		
Nominal width	[mm]	4.6	4.3		5.6														
Standard nominal flow rate	[l/min]	600	580	470	450	630	680	600	580	580									
Flow rate on manifold rail G1/8	[l/min]	510		430	410	520	570	520	500	460									
<b>Switching time</b>																			
VUVG-...	On/off	[ms]	9/25	12/18		14/22	-	13/37	12/40										
	Changeover	[ms]	-				8		14										
VUVG-...-P1	On/off	[ms]	11/18	14/13		16/16	-	12/26	14/24										
	Changeover	[ms]	-	-		-	12	-	19										
Pneumatic connection	1, 3, 5	G1/4 in manifold rail																	
	2, 4	G1/8 in manifold rail																	
	12/14, 82/84	M5 in manifold rail																	
Product weight	VUVG...	[g]	89	80	78	89	70	89											
	VUVG-...-P1	[g]	65	56	66	65	58	65											
Certification	VUVG...	c UL us - Recognized (OL) RCM																	
	CE marking (see declaration of conformity) <sup>5)</sup>	To EU EMC Directive To EU Low Voltage Directive																	
Corrosion resistance class CRC <sup>6)</sup>		2																	

1) C=Normally closed/mid-position closed

2) U=Normally open/mid-position pressurised

3) E=Mid-position exhausted

4) H=2x 3/2-way valve in one housing with 1x normally closed and 1x normally open

5) For information about the area of use, see the EC declaration of conformity at: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/) → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

6) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

## Data sheet

Operating and environmental conditions		T32-A <sup>1)</sup>	T32-M <sup>2)</sup>	M52-A <sup>1)</sup>	B52	M52-M <sup>2)</sup>	P53
Valve function							
Operating medium		Compressed air to ISO 8573-2010 [7:4:4]					
Operating pressure	Internal VUVG-...	[MPa]	0.15 ... 0.8	0.35 ... 0.8	0.25 ... 0.8	0.15 ... 0.8	0.3 ... 0.8
		[bar]	1.5 ... 8	3.5 ... 8	2.5 ... 8	1.5 ... 8	3 ... 8
	External	[MPa]	0.15 ... 1	-0.09 ... 1		-0.09 ... 0.8	-0.09 ... 1
		[bar]	1.5 ... 10	-0.9 ... 10		-0.9 ... 8	-0.9 ... 10
Pilot pressure <sup>3)</sup>		[MPa]	0.15 ... 0.8	0.3 ... 0.8	0.25 ... 0.8	0.15 ... 0.8	0.3 ... 0.8
		[bar]	1.5 ... 8	3 ... 8	2.5 ... 8	1.5 ... 8	3 ... 8
Ambient temperature	VUVG-...	[°C]	-5 ... +50, with holding current reduction -5 ... +60				
	VUVG-...-P1	[°C]	-5 ... +50 for mounting on manifold rail -5 ... +60				
Temperature of medium	VUVG-...	[°C]	-5 ... +50, with holding current reduction -5 ... +60				
	VUVG-...-P1	[°C]	-5 ... +50 for mounting on manifold rail -5 ... +60				

1) Pneumatic spring

2) Mechanical spring

3) Minimum pilot pressure 50% of operating pressure

## Electrical data

Electrical connection	VUVG-...	Via E-box → page 102
	VUVG-...-P1	Via electric pilot valve
Pilot interface	VUVG-...-P1	To ISO 15218
Operating voltage	VUVG-...	[V DC] 5, 12 and 24 ±10%
	VUVG-...-P1	[V DC] 12 and 24 ±10%
		[V AC] 24, 110 and 230 ±10%
Power	VUVG-...	[W] 1, reduced to 0.35 with holding current reduction
	VUVG-...-P1	[W] 1.3
Duty cycle ED	[%]	100
Degree of protection to EN 60529		
	VUVG-...	IP40 (with plug socket), IP65 (with M8)
	VUVG-...-P1	IP65, with electric pilot valve and plug socket

## Information on materials

Housing	Wrought aluminium alloy
Seals	HNBR, NBR
Note on materials	RoHS-compliant



## Data sheet

## Dimensions VUVG

2x 3/2-way, 5/2-way and 5/3-way valve

Download CAD data → [www.festo.com](http://www.festo.com)

5/2-way valve, single solenoid



-  **Note**  
More dimensions  
E-boxes  
→ Page 102




[1] Horizontal electrical connection      [2] Manual override

Type	B1	H1	L1	L2	L3	L4	L5	L6	L7	L8
VUVG-B14-....F ...	14	34.8	107	102	8	66.5	4.9	6.2	89.5	87

## Dimensions VUVG-... -P1

2x 3/2-way, 5/2-way and 5/3-way valve

5/2-way valve, single solenoid





[4] Ports 1, 3 and 5


[5] Ports 2 and 4

Type	B1	H2	L1	L2	L11
VUVG-B14-...P1	14.4	34.8	105.2	66.5	88.6

## Ordering data

Ordering data		Description	Part no.	Type
<b>Sub-base valve G1/8, without E-box</b>				
	<b>2x 3/2-way valve</b>			
	External pilot air supply	Normally closed, pneumatic spring reset	566513	VUVG-B14-T32C-AZT-F-1P3
		Normally open, pneumatic spring reset	566514	VUVG-B14-T32U-AZT-F-1P3
		1x normally open, 1x normally closed, pneumatic spring reset	566515	VUVG-B14-T32H-AZT-F-1P3
		Normally closed, mechanical spring reset	574376	VUVG-B14-T32C-MZT-F-1P3
		Normally open, mechanical spring reset	574377	VUVG-B14-T32U-MZT-F-1P3
		5/2-way single solenoid valve	1x normally open, 1x normally closed, mechanical spring reset	574378
	Pneumatic spring reset		566516	VUVG-B14-M52-AZT-F-1P3
	Mechanical spring reset		574379	VUVG-B14-M52-MZT-F-1P3
	5/2-way double solenoid valve			
External pilot air supply		566517	VUVG-B14-B52-ZT-F-1P3	
<b>5/3-way valve</b>				
External pilot air supply	Mid-position closed, mechanical spring reset	566518	VUVG-B14-P53C-ZT-F-1P3	
	Mid-position exhausted, mechanical spring reset	566519	VUVG-B14-P53E-ZT-F-1P3	
	Mid-position pressurised, mechanical spring reset	566520	VUVG-B14-P53U-ZT-F-1P3	
<b>Sub-base valve G1/8, with E-box R8</b>				
	<b>2x 3/2-way valve</b>			
	External pilot air supply	Normally closed, pneumatic spring reset	574242	VUVG-B14-T32C-AZT-F-1R8L
		Normally open, pneumatic spring reset	574243	VUVG-B14-T32U-AZT-F-1R8L
		1x normally open, 1x normally closed, pneumatic spring reset	574244	VUVG-B14-T32H-AZT-F-1R8L
		Normally closed, mechanical spring reset	578248	VUVG-B14-T32C-MZT-F-1R8L
		Normally open, mechanical spring reset	8031517	VUVG-B14-T32U-MZT-F-1R8L
		5/2-way single solenoid valve	1x normally open, 1x normally closed, mechanical spring reset	8031518
	Pneumatic spring reset		574245	VUVG-B14-M52-AZT-F-1R8L
	Mechanical spring reset		578158	VUVG-B14-M52-MZT-F-1R8L
	5/2-way double solenoid valve			
External pilot air supply		574246	VUVG-B14-B52-ZT-F-1R8L	
<b>5/3-way valve</b>				
External pilot air supply	Mid-position closed, mechanical spring reset	574247	VUVG-B14-P53C-ZT-F-1R8L	
	Mid-position exhausted, mechanical spring reset	574249	VUVG-B14-P53E-ZT-F-1R8L	
	Mid-position pressurised, mechanical spring reset	574248	VUVG-B14-P53U-ZT-F-1R8L	

## Ordering data

Ordering data		Description	Part no.	Type
<b>Sub-base valve G1/8, to ISO 15218</b>				
	<b>2x 3/2-way valve</b>			
	External pilot air supply	Normally closed, pneumatic spring reset	8033535	VUVG-B14-T32C-AZ-F-P1
		Normally open, pneumatic spring reset	8033536	VUVG-B14-T32U-AZ-F-P1
		1x normally open, 1x normally closed, pneumatic spring reset	8033537	VUVG-B14-T32H-AZ-F-P1
		Normally closed, mechanical spring reset	8033538	VUVG-B14-T32C-MZ-F-P1
		Normally open, mechanical spring reset	8033539	VUVG-B14-T32U-MZ-F-P1
		5/2-way valve, single solenoid	1x normally open, 1x normally closed, mechanical spring reset	8033540
	Pneumatic spring reset		8033541	VUVG-B14-M52-AZ-F-P1
	Mechanical spring reset		8033542	VUVG-B14-M52-MZ-F-P1
	<b>5/2-way, valve, double solenoid</b>			
External pilot air supply	8033543	VUVG-B14-B52-Z-F-P1		
<b>5/3-way valve</b>				
External pilot air supply	Mid-position closed, mechanical spring reset	8033544	VUVG-B14-P53C-Z-F-P1	
	Mid-position exhausted, mechanical spring reset	8033545	VUVG-B14-P53E-Z-F-P1	
	Mid-position pressurised, mechanical spring reset	8033546	VUVG-B14-P53U-Z-F-P1	


## Manifold assembly

**Sub-base valve for  
manifold assembly  
Connection G1/8**



### Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



- - Note

Additional dimensions

E-boxes

→ Page 104

[1] Ports 1, 3 and 5: G1/4 (at both ends)

[5] Electrical connection for E-boxes and accessories

[6] H-rail mounting (two M4x35 screws are required for mounting)

[7] Cover plate

[2] Ports 2, 4: G1/8

[8] Supply plate: ports 1, 3 and 5: G1/8

[3] Ports 12, 14: M5

[9] Valves/cover plate mounting on manifold rail: M2.5 thread


Type	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12
VABM-L1-14W-G14	118.3	95.1	67.7	58.2	56.3	36.6	16.7	4.5	72.9	26.5	20	49.1

Type	B13	D1	D2	D3	D4	H1	H2	H3	H4	H5
VABM-L1-14W-G14	49.1	G1/4	G1/8	M5	Ø 4.5	64.3	19.6	15.3	10.1	29.5

Type	H6	H7	H8	H9	H10	H11	H12	L3	L5	L6	L7	L8	L9	L10	L11
VABM-L1-14W-G14	9.8	4.8	22.1	7	15.4	6.8	23.9	6	1	16	14.4	11.3	18.5	16	14

Valve positions	2	3	4	5	6	7	8	9	10	12	14	16
L1	56.3	72.3	88.3	104.3	120.3	136.3	152.3	168.3	184.3	216.3	248.3	280.3
L2	40	56	72	88	104	120	136	152	168	200	232	264
L4	54.3	70.3	86.3	102.3	118.3	134.3	150.3	166.3	182.3	214.3	246.6	278.3
VABM weight [g]	232	306	380	454	528	602	676	750	824	972	1120	1268

## Ordering data

Technical data – Manifold rails <sup>1)</sup>			Connection	CRC	Material <sup>3)</sup>	Operating pressure		Max. tightening torque for assembly [Nm]		
	2, 4	1, 3, 5	12/14, 82/84			[MPa]	[bar]	Valve	H-rail	Wall
	G1/8	G1/4	M5	2 <sup>2)</sup>	Wrought aluminium alloy	-0.09 ... 1	-0.9 ... 10	0.65	1.5	3


1) Blanking plugs are included with the manifold rail.

2) Corrosion resistance class CRC 2 to Festo standard FN 940070



Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

3) Note on materials: RoHS-compliant.

### Ordering data – Manifold rail

Description	Part no.	Type
<b>Manifold rail for sub-base valve G1/8</b>		
	For size B14 (G1/8)	2 valve positions
		★ 566642
		VABM-L1-14W-G14-2
		3 valve positions
		★ 566643
		VABM-L1-14W-G14-3
		4 valve positions
		★ 566644
		VABM-L1-14W-G14-4
		5 valve positions
		566645
		VABM-L1-14W-G14-5
		6 valve positions
		★ 566646
		VABM-L1-14W-G14-6
		7 valve positions
		566647
		VABM-L1-14W-G14-7
		8 valve positions
		★ 566648
		VABM-L1-14W-G14-8
		9 valve positions
		566649
		VABM-L1-14W-G14-9
		10 valve positions
		★ 566650
		VABM-L1-14W-G14-10
		12 valve positions
		566651
		VABM-L1-14W-G14-12
		14 valve positions
		566652
		VABM-L1-14W-G14-14
		16 valve positions
		566653
		VABM-L1-14W-G14-16

### Ordering data – Accessories

Description	Part no.	Type
Cover plate Data sheets → Internet: vabb		
	For valve position on manifold rail, including screws and seal	★ 569989
Separator Data sheets → Internet: vabd		
	For creating pressure zones	569996
Supply plate Data sheets → Internet: vabf		
	For valve position on manifold rail, including screws and seal	569993
Seals Data sheets → Internet: vabd		
	For sub-base valves G1/8 Delivery quantity: 10 sets (each with 2 screws and 1 seal)	566676
		VABD-L1-14B-S-G18

## Data sheet

## Function

2x 3/2C, 2x 3/2U, 2x 3/2H

 Size 18 mm

5/2-way, single solenoid

 Flow rate

800 ... 1080 l/min

5/2-way, double solenoid valve

 Voltage

5, 12 and 24 V DC

5/3C, 5/3U, 5/3E

Circuit symbols → page 13



## General technical data VUVG-B

Valve function	T32-A	T32-M	M52-R	B52	M52-M	P53					
Normal position	C <sup>1)</sup> U <sup>2)</sup> H <sup>4)</sup>	C <sup>1)</sup> U <sup>2)</sup> H <sup>4)</sup>	–	–	–	C <sup>1)</sup> U <sup>2)</sup> E <sup>3)</sup>					
Stable position	Monostable			Bistable	Monostable	Monostable					
Pneumatic spring reset	Yes	No	Yes <sup>5)</sup>	–	No	–					
Mechanical spring reset	No	Yes	Yes <sup>5)</sup>	–	Yes	Yes					
Vacuum operation at port 1	No	Only with external pilot air supply									
Design	Piston spool										
Sealing principle	Soft										
Type of actuation	Electrical										
Type of control	Piloted										
Pilot air supply	External, internal; can be selected via sub-base										
Exhaust function	Can be throttled										
Manual override	Choice of non-detenting, covered, non-detenting/detenting or detenting										
Type of mounting	On manifold rail										
Mounting position	Any										
Nominal width	[mm]	5.7	6.9	7.3	6.9	6.5					
Standard nominal flow rate	[l/min]	900	1150			1080					
Flow rate on manifold rail		800	1000			950					
Switching time on/off	[ms]	13/27	15/22	15/31	–	10/45					
Switching time changeover	[ms]	–		11		29					
Size	[mm]	18									
Connection	1, 3, 5 2, 4 12/14, 82/84	G3/8 in manifold rail G1/4 in manifold rail M5 in manifold rail									
Product weight	[g]	164	154	160	154	160					
Certification		c UL us - Recognized (OL) c CSA us (OL) RCM compliance mark									
CE marking (see declaration of conformity) <sup>6)</sup>	To EU EMC Directive										
Corrosion resistance class CRC <sup>7)</sup>	2										

1) C=Normally closed/mid-position closed

2) U=Normally open/mid-position pressurised

3) E=Mid-position exhausted

4) H=2x 3/2-way valve in one housing with 1x normally closed and 1x normally open

5) Combined reset method

6) For information about the area of use, see the EC declaration of conformity at: [www.festo.com/catalogue/...](http://www.festo.com/catalogue/) → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

7) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

## Data sheet

Operating and environmental conditions		T32-A <sup>1)</sup>	T32-M <sup>3)</sup>	M52-R <sup>2)</sup>	B52	M52-M <sup>3)</sup>	P53	
Valve function								
Operating medium	Compressed air to ISO 8573-2010 [7:4:4]							
Operating pressure	Internal	[MPa]	0.15 ... 0.8	0.3 ... 0.8	0.25 ... 0.8	0.15 ... 0.8	0.3 ... 0.8	
		[bar]	1.5 ... 8	3 ... 8	2.5 ... 8	1.5 ... 8	3 ... 8	
	External	[MPa]	0.15 ... 1	-0.09 ... 1		-0.09 ... 1	-0.09 ... 1	
		[bar]	1.5 ... 10	-0.9 ... 10		-0.9 ... 10	-0.9 ... 10	
Pilot pressure	[MPa]	0.15 ... 0.8	0.2 ... 0.8	0.25 ... 0.8	0.15 ... 0.8	0.3 ... 0.8		
[bar]		1.5 ... 8	2 ... 8	2.5 ... 8	1.5 ... 8	3 ... 8		
Ambient temperature	[°C]	-5 ... +50, with holding current reduction	-5 ... +60					
Temperature of medium	[°C]	-5 ... +50, with holding current reduction	-5 ... +60					

1) Pneumatic spring

2) Mixed, pneumatic/mechanical spring

3) Mechanical spring

### Electrical data


Electrical connection	Via E-box → page 102
Operating voltage	[V DC] 5, 12 and 24 ±10%
Power	[W] 1, reduced to 0.35 with holding current reduction
Duty cycle	[%] 100
Degree of protection to EN 60529	IP40 (with plug socket), IP65 (with M8)

### Information on materials

Housing	Wrought aluminium alloy
Seals	HNBR, NBR
Note on materials	RoHS-compliant

### Dimensions

2x 3/2-way, 5/2-way and 5/3-way valve

Download CAD data → [www.festo.com](http://www.festo.com)

- - Note

Additional dimensions



E-boxes

→ Page 104

[1] Horizontal electrical connection      [2] Manual override


Type	B1	H1	L1	L2	L3	L4	L5
VUVG-B18-...-F...	18.3	43.1	129.4	124.4	86.4	112.2	109.7

## Ordering data

Ordering data		Description	Part no.	Type	
<b>Sub-base valve G1/4, without E-box</b>					
	<b>2x 3/2-way valve</b>				
	External pilot air supply	Normally closed, pneumatic spring reset	574443	VUVG-B18-T32C-AZT-F-1P3	
		Normally open, pneumatic spring reset	574444	VUVG-B18-T32U-AZT-F-1P3	
		1x normally open, 1x normally closed, pneumatic spring reset	574445	VUVG-B18-T32H-AZT-F-1P3	
		Normally closed, mechanical spring reset	574446	VUVG-B18-T32C-MZT-F-1P3	
		Normally open, mechanical spring reset	574447	VUVG-B18-T32U-MZT-F-1P3	
		<b>5/2-way single solenoid valve</b>	1x normally open, 1x normally closed, mechanical spring reset	574448	VUVG-B18-T32H-MZT-F-1P3
	External pilot air supply		Pneumatic/mechanical spring reset	574449	VUVG-B18-M52-RZT-F-1P3
			Mechanical spring reset	574450	VUVG-B18-M52-MZT-F-1P3
	<b>5/2-way double solenoid valve</b>				
	External pilot air supply			574451	VUVG-B18-B52-ZT-F-1P3
	<b>5/3-way valve</b>				
External pilot air supply	Mid-position closed, mechanical spring reset	574452	VUVG-B18-P53C-ZT-F-1P3		
	Mid-position exhausted, mechanical spring reset	574453	VUVG-B18-P53E-ZT-F-1P3		
	Mid-position pressurised, mechanical spring reset	574454	VUVG-B18-P53U-ZT-F-1P3		
<b>Sub-base valve G1/4, with E-box R8</b>					
	<b>2x 3/2-way valve</b>				
	External pilot air supply	Normally closed, pneumatic spring reset	8031537	VUVG-B18-T32C-AZT-F-1R8L	
		Normally open, pneumatic spring reset	8031538	VUVG-B18-T32U-AZT-F-1R8L	
		1x normally open, 1x normally closed, pneumatic spring reset	8031539	VUVG-B18-T32H-AZT-F-1R8L	
		Normally closed, mechanical spring reset	8031540	VUVG-B18-T32C-MZT-F-1R8L	
		Normally open, mechanical spring reset	8031541	VUVG-B18-T32U-MZT-F-1R8L	
		<b>5/2-way single solenoid valve</b>	1x normally open, 1x normally closed, mechanical spring reset	8031542	VUVG-B18-T32H-MZT-F-1R8L
	External pilot air supply		Pneumatic/mechanical spring reset	8031543	VUVG-B18-M52-RZT-F-1R8L
			Mechanical spring reset	8031544	VUVG-B18-M52-MZT-F-1R8L
	<b>5/2-way double solenoid valve</b>				
	External pilot air supply			8031545	VUVG-B18-B52-ZT-F-1R8L
	<b>5/3-way valve</b>				
External pilot air supply	Mid-position closed, mechanical spring reset	8031546	VUVG-B18-P53C-ZT-F-1R8L		
	Mid-position exhausted, mechanical spring reset	8031547	VUVG-B18-P53E-ZT-F-1R8L		
	Mid-position pressurised, mechanical spring reset	8031548	VUVG-B18-P53U-ZT-F-1R8L		

## Manifold assembly

**Sub-base valve for  
manifold assembly  
Connection G1/4**




### Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)

- - Note

Additional dimensions  
E-boxes  
→ Page 104



[1] Ports 1, 3 and 5: G3/8 (at both ends)

[2] Ports 2, 4: G1/4

[3] Ports 12, 14: M5

[4] Ports 82, 84: M5

[5] Electrical connection for E-boxes and accessories

[6] H-rail mounting (two M4x40 screws are required for mounting)


[7] Cover plate

[8] Supply plate, ports 1, 3 and 5: G1/4

[9] Valve/cover plate/supply plate mounting on manifold rail: M3 thread

Type	B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	D1
VABM-L1-18W-G38	129.4	124.4	95.6	73.1	47.8	22.5	51.7	34.8	26	90.6	76.8	4.5
Type	H1	H2	H3	H4	H5	H6	H7	H8	H9	H10	H11	H12
VABM-L1-18W-G38	81.6	38.5	11.5	28.4	27.6	19	12	12.1	6.1	29.1	8.8	6.5
Type	L3	L4	L5	L6	L7	L8	L9	L10				
VABM-L1-18W-G38	6	23	19	20.8	19	15.6	8.5	1				
Valve positions	2	3	4	5	6	7	8	9	10	12	14	16
L1	63.5	82.5	101.5	120.5	139.5	158.5	177.5	196.5	215.5	253.5	291.5	329.5
L2	49	68	87	106	125	144	163	182	201	239	277	315
VABM weight [g]	232	306	380	454	528	602	676	750	824	972	1120	1268

## Ordering data


Technical data – Manifold rails <sup>1)</sup>		Connection		CRC	Material <sup>3)</sup>	Operating pressure		Max. tightening torque for assembly [Nm]		
		2, 4	1, 3, 5	12/14, 82/84		[MPa]	[bar]	Valve	H-rail	Wall
	G1/4	G3/8	M5	2 <sup>2)</sup>	Wrought aluminium alloy	-0.09 ... 1	-0.9 ... 10	1.18	1.5	3

1) Blanking plugs are included with the manifold rail.


2) Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements which are in direct contact with a normal industrial environment.

3) Note on materials: RoHS-compliant.

Ordering data – Manifold rails		Description	Part no.	Type
<b>Manifold rail for sub-base valve G1/4</b>				
	For size B18 (G1/4)	2 valve positions	574467	VABM-L1-18W-G38-2
		3 valve positions	574468	VABM-L1-18W-G38-3
		4 valve positions	574469	VABM-L1-18W-G38-4
		5 valve positions	574470	VABM-L1-18W-G38-5
		6 valve positions	574471	VABM-L1-18W-G38-6
		7 valve positions	574472	VABM-L1-18W-G38-7
		8 valve positions	574473	VABM-L1-18W-G38-8
		9 valve positions	574474	VABM-L1-18W-G38-9
		10 valve positions	574475	VABM-L1-18W-G38-10
		12 valve positions	574476	VABM-L1-18W-G38-12
		14 valve positions	574477	VABM-L1-18W-G38-14
		16 valve positions	574478	VABM-L1-18W-G38-16

## Ordering data

Ordering data – Accessories		Description	Part no.	Type
Cover plate				Data sheets → Internet: vabb
	For valve position on manifold rail, including screws and seal	★ 574482	VABB-L1-18	
Separator				Data sheets → Internet: vabd
	For creating pressure zones	574483	VABD-14-B	
Supply plate				Data sheets → Internet: vabf
	For valve position on manifold rail, including screws and seal	574481	VABF-L1-18-P3A4-G14	
Seals				Data sheets → Internet: vabd
	For sub-base valves G1/4	Delivery quantity: 10 sets (each with 2 screws and 1 seal)	574480	VABD-L1-18B-S-G14




**Note**  
Connect supply plate at port 1 with compressed air. Reverse operation (pressure at port 3, 5) is not permissible.

## E-boxes


General technical data		H2	H3	S2	S3	L-	R1	R8
Variants								
Mounting position		Any						
Electrical connection		2-pin, socket			Flying leads	Individual plug M8, 4-pin	Individual plug M8, 3-pin	
Degree of protection		IP40				IP65		
Signal status display		LED						
Type of mounting		Clip				Self-tapping screw		
Note on materials		RoHS-compliant						
Housing colour		Black						
Information on housing materials		PA						
Certification		RCM compliance mark						

## Protective circuit without holding current reduction



The solenoid coils (P type) of the 5, 12 and 24 V designs have a protective circuit to arrest sparks and protect against polarity reversal.

## Protective circuit with holding current reduction




The 24 V DC design (R type) additionally features holding current reduction. This reduces the power from 1 W to 0.35 W.

## Pin allocation for E-box

	Pin	Description
<b>Rectangular plug, connection pattern H</b>		
	VAVE-L1-1VH2-LP, VAVE-L1-1VH3-LP	
2 + + 1	1 + or -	Without holding current reduction
2 + + 1	2 + or -	
<b>VAVE-L1-1H2-LR, VAVE-L1-1H3-LR</b>		
2 + + 1	1 +	With holding current reduction
2 + + 1	2 -	
<b>Rectangular plug, connection pattern S</b>		
	VAVE-L1-1VS2-LP, VAVE-L1-1VS3-LP	
2 + + 1	1 + or -	Without holding current reduction
2 + + 1	2 + or -	
<b>VAVE-L1-1S2-LR, VAVE-L1-1S3-LR</b>		
2 + + 1	1 -	With holding current reduction
2 + + 1	2 +	
<b>Flying leads, 2-pin</b>		
	VAVE-L1-1VL1...4-LP	
1 2	1 + or -	Without holding current reduction
1 2	2 + or -	
<b>VAVE-L1-1L1...4-LR</b>		
1 2	1 -	With holding current reduction
1 2	2 +	


## E-boxes

Pin allocation for E-box		Pin	Description
<b>Round plug, M8, 3-pin</b>			
	<b>VAVE-L1-1VR8-LP</b>	1	Not used
		3	+ or -
		4	+ or -
<b>VAVE-L1-1R8-LR</b>			
		1	Not used
		3	+ or -
		4	+ or -
<b>Round plug, M8, 4-pin</b>			
	<b>VAVE-L1-1VR1-LP</b>	1	Not used
		2	Not used
		3	+ or -
		4	+ or -
<b>VAVE-L1-1R1-LR</b>			
		1	Not used
		2	Not used
		3	+ or -
		4	+ or -
<b>Open cable end</b>			
	<b>VAVE-L1-1VK...</b>	BK	+ or -
		BK	+ or -
<b>VAVE-L1-1K...</b>			
		BK	+ or -
		BK	+ or -


## E-boxes

### Dimensions

E-boxes, S2/H2



E-boxes, S3/H3




Download CAD data → [www.festo.com](http://www.festo.com)

Type	B1	H1 ±0.5	L1	L2	L3
VAVE-L1-1VS2-LP	9.8	28.8	12.9	5.2	6.5
VAVE-L1-1S2-LR					
VAVE-L1-1VH2-LP			10.8		
VAVE-L1-H2-LR					


Type	B1	H1 ±0.5	L1	L2	L3
VAVE-L1-1VS3-LP	9.8	35	7.6	5.2	6.5
VAVE-L1-1S3-LR					
VAVE-L1-1VH3-LP		33.6	7.5		
VAVE-L1-1H3-LR					

### Dimensions

E-boxes, VL11 ... 14



E-boxes, VK6 ... 9



Download CAD data → [www.festo.com](http://www.festo.com)


Type	B1	H1 ±0.5	L1	L2	L3
VAVE-L1-1VL1-LP	9.8	28.8	7.9	0.5	6.5
VAVE-L1-1L1-LR					
VAVE-L1-1VL2-LP				1	
VAVE-L1-1L2-LR					
VAVE-L1-1VL3-LP				2.5	
VAVE-L1-1L3-LR					
VAVE-L1-1VL4-LP				5	
VAVE-L1-1L4-LR					

Type	B1	H1	H2 ±0.3	L1	L2 ±5	L3 ±0.5	D1 Ø
VAVE-L1-1VK6-LP	9.8	15.3	11.8	0.5	50	28.7	1.8
VAVE-L1-1VK7-LP				1.0			
VAVE-L1-1VK8-LP				2.5			
VAVE-L1-1VK9-LP				5.0			
VAVE-L1-1K6-LR				0.5			
VAVE-L1-1K7-LR				1.0			
VAVE-L1-1K8-LR				2.5			
VAVE-L1-1K9-LR				5.0			

## E-boxes

## Dimensions

E-boxes, R8/R1


Download CAD data → [www.festo.com](http://www.festo.com)

Type	B1	H1	H2	H3	L1	L2	L3	L4	D1 Ø
VAVE-L1-1VR8-LP	9.8	28.7	13.7	20.2	18.4	9.9	9.7	8.6	M8
VAVE-L1-1VR1-LP									








## Ordering data – E-boxes

Design	Plugs	Additional functions	Ambient temperature [°C]	Code	Power [W]	Voltage [V DC]	Part no.	Type
	NEBV-H1 ...	Spark arresting, bipolar, IP40	-5 ... +50	H2	1	12/24	<b>★ 566714</b>	VAVE-L1-1VH2-LP
		Spark arresting, holding current reduction, IP40	-5 ... +60	H2R	0.35	24	<b>★ 566716</b>	VAVE-L1-1H2-LR
	NEBV-H1 ...	Spark arresting, bipolar, IP40	-5 ... +50	H3	1	12/24	<b>566715</b>	VAVE-L1-1VH3-LP
		Spark arresting, holding current reduction, IP40	-5 ... +60	H3R	0.35	24	<b>566717</b>	VAVE-L1-1H3-LR
	NEBV-HS ...	Spark arresting, bipolar, IP40	-5 ... +50	S2	1	12/24	<b>566718</b>	VAVE-L1-1VS2-LP
		Spark arresting, holding current reduction, IP40	-5 ... +60	S2R	0.35	24	<b>566720</b>	VAVE-L1-1S2-LR
	NEBV-HS ...	Spark arresting, bipolar, IP40	-5 ... +50	S3	1	12/24	<b>566719</b>	VAVE-L1-1VS3-LP
		Spark arresting, holding current reduction, IP40	-5 ... +60	S3R	0.35	24	<b>566721</b>	VAVE-L1-1S3-LR
	Open cable end	Spark arresting, bipolar, IP40	-5 ... +50	L1	1	12/24	<b>566722</b>	VAVE-L1-1VL1-LP
				L2			<b>566723</b>	VAVE-L1-1VL2-LP
				L3			<b>566724</b>	VAVE-L1-1VL3-LP
				L4			<b>566725</b>	VAVE-L1-1VL4-LP
		Spark arresting, holding current reduction, IP40	-5 ... +60	L1R	0.35	24	<b>566726</b>	VAVE-L1-1L1-LR
				L2R			<b>566727</b>	VAVE-L1-1L2-LR
				L3R			<b>566728</b>	VAVE-L1-1L3-LR
				L4R			<b>566729</b>	VAVE-L1-1L4-LR

## E-boxes

Ordering data – E-boxes									
Design	Plugs	Additional functions	Ambient temperature [°C]	Code	Power [W]	Voltage [V DC]	Cable length [m]	Part no.	Type
	Open cable end	Spark arresting, bipolar, IP65	-5 ... +60	K6	1	12/24	0.5	573941	VAVE-L1-1VK6-LP
				K7			1	573942	VAVE-L1-1VK7-LP
				K8			2.5	573943	VAVE-L1-1VK8-LP
				K9			5	573944	VAVE-L1-1VK9-LP
	NEBU-M8 ...	Spark arresting, bipolar, holding current reduction, IP65	-5 ... +60	K6R	0.35	24	0.5	573945	VAVE-L1-1K6-LR
				K7R			1	573946	VAVE-L1-1K7-LR
				K8R			2.5	573947	VAVE-L1-1K8-LR
				K9R			5	573948	VAVE-L1-1K9-LR
	NEBU-M8 ...	Spark arresting, bipolar, IP65	-5 ... +60	R8	1	12/24	-	573919	VAVE-L1-1VR8-LP
		Spark arresting, bipolar, holding current reduction, IP65		R8R	0.35	24	-	573920	VAVE-L1-1R8-LR
		Spark arresting, bipolar, IP65		R1	1	12/24	-	573921	VAVE-L1-1VR1-LP
		Spark arresting, bipolar, holding current reduction, IP65		R1R	0.35	24	-	573922	VAVE-L1-1R1-LR

## Accessories



Ordering data		Description	Cable length [m]	Part no.	Type
Plug socket with cable, not sheathed, open end					Data sheets → Internet: nebv
	For E-box code H2, H2R or H3, H3R, 2-pin socket		0.5	566654	NEBV-H1G2-KN-0.5-N-LE2
			1	566655	NEBV-H1G2-KN-1-N-LE2
			2.5	566656	NEBV-H1G2-KN-2.5-N-LE2
			5	566657	NEBV-H1G2-KN-5-N-LE2
Plug socket with cable, sheathed, open end					Data sheets → Internet: nebv
	For E-box code H2, H2R or H3, H3R, 2-pin socket		0.5	566658	NEBV-H1G2-P-0.5-N-LE2
			1	566659	NEBV-H1G2-P-1-N-LE2
			2.5	566660	NEBV-H1G2-P-2.5-N-LE2
			5	566661	NEBV-H1G2-P-5-N-LE2
Plug socket with cable, not sheathed, open end					Data sheets → Internet: nebv
	For E-box code S2, S2R or S3, S3R, 2-pin socket		0.5	566662	NEBV-HSG2-KN-0.5-N-LE2
			1	566663	NEBV-HSG2-KN-1-N-LE2
			2.5	566664	NEBV-HSG2-KN-2.5-N-LE2
			5	566665	NEBV-HSG2-KN-5-N-LE2
Plug socket with cable, sheathed, open end					Data sheets → Internet: nebv
	For E-box code S2, S2R or S3, S3R, 2-pin socket		0.5	566666	NEBV-HSG2-P-0.5-N-LE2
			1	566667	NEBV-HSG2-P-1-N-LE2
			2.5	566668	NEBV-HSG2-P-2.5-N-LE2
			5	566669	NEBV-HSG2-P-5-N-LE2
Connecting cable, open end					
	For pilot valve VSCS to ISO 15218, narrow socket, type C to EN 175301-803		2.5	8032623	NEBV-C1SW2L-P-K-2.5-N-LE2-S9
			5	8032626	NEBV-C1SW2L-P-K-5-N-LE2-S9
			10	8032627	NEBV-C1SW2L-P-K-10-N-LE2-S9
			2.5	8032628	NEBV-C1SW3-K-2.5-N-LE3-S9
			5	8032629	NEBV-C1SW3-K-5-N-LE3-S9
Connecting cable, open end					Data sheets → Internet: nebu
	For E-box code R8 3-pin, straight socket, M8x1		2.5	541333	NEBU-M8G3-K-2.5-LE3
			5	541334	NEBU-M8G3-K-5-LE3
	For E-box code R1 4-pin, straight socket, M8x1		2.5	541342	NEBU-M8G4-K-2.5-LE4
			5	541343	NEBU-M8G4-K-5-LE4
Connecting cable, open end					Data sheets → Internet: nebu
	For E-box code R8 3-pin, angled socket, M8x1		2.5	541338	NEBU-M8W3-K-2.5-LE3
			5	541341	NEBU-M8W3-K-5-LE3
	For E-box code R1 4-pin, angled socket, M8x1		2.5	541344	NEBU-M8W4-K-2.5-LE4
			5	541345	NEBU-M8W4-K-5-LE4
Connecting cable					Data sheets → Internet: nebu
	For E-box code R8, 3-pin, straight socket, M8x1		0.5	541346	NEBU-M8G3-K-0.5-M8G3
			1	541347	NEBU-M8G3-K-1-M8G3
			2.5	541348	NEBU-M8G3-K-2.5-M8G3
			5	541349	NEBU-M8G3-K-5-M8G3
	For E-box code R1, 4-pin, straight socket, M8x1		10	569844	NEBU-M8G3-K-10-M8G3
			2.5	554035	NEBU-M8G4-K-2.5-M8G4
Connecting cable, open end					Data sheets → Internet: nebu
	For pilot valve VSCS to ISO 15218, straight socket, M12x1, A-coded to EN 61076-2-101		2.5	541363	NEBU-M12G5-K-2.5-LE3
			5	541364	NEBU-M12G5-K-5-LE3
	For pilot valve VSCS to ISO 15218, angled socket, M12x1, A-coded to EN 61076-2-101		2.5	541367	NEBU-M12W5-K-2.5-LE3
			5	541370	NEBU-M12W5-K-5-LE3

## Accessories

Ordering data		Description	Part no.	Type	PU <sup>1)</sup>
<b>Blanking plug</b>					
	For manifold rail and valve	M5 thread	3843	B-M5	10
		M7 thread	174309	B-M7	10
	For manifold rail	G1/8 thread	3568	B-1/8	10
		G1/4 thread	3569	B-1/4	10
		G3/8 thread	3570	B-3/8	10
	For valve	G1/8 thread	578406	NPQH-BK-G18-P10	10
		G1/4 thread	578407	NPQH-BK-G14-P10	10
<b>Reducing nipple</b>					
	M7 male thread	M5 female thread	161359	D-M5I-M7A-ISK	10
<b>Fittings</b>					
	M3 thread	For tubing Ø 3 mm	133001	QSM-M3-3-I-R	10
		For tubing Ø 4 mm	133002	QSM-M3-4-I-R	10
	M5 thread	For tubing Ø 3 mm	133003	QSM-M5-3-I-R	10
		Oval releasing ring	153313	QSM-M5-3-I	10
		For tubing Ø 4 mm	133004	QSM-M5-4-I-R	10
		Oval releasing ring	153315	QSM-M5-4-I	10
		For tubing Ø 6 mm	133005	QSM-M5-6-I-R	10
		Oval releasing ring	153317	QSM-M5-6-I	10
	M7 thread	For tubing Ø 4 mm	153319	QSM-M7-4-I	10
		For tubing Ø 6 mm	133007	QSM-M7-6-I-R	10
		Oval releasing ring	153321	QSM-M7-6-I	10
	G1/8 thread	For tubing Ø 4 mm	186106	QS-G1/8-4-I	10
		For tubing Ø 6 mm	186107	QS-G1/8-6-I	10
		For tubing Ø 8 mm	186109	QS-G1/8-8-I	10
		For tubing Ø 10 mm	132999	QS-G1/8-10-I	10
	G1/4 thread	For tubing Ø 6 mm	186108	QS-G1/4-6-I	10
			130677	QS-1/4-6-100	100
		For tubing Ø 8 mm	186110	QS-G1/4-8-I	10
			153016	QS-1/4-8-I	10
		For tubing Ø 10 mm	186112	QS-G1/4-10-I	10
			153018	QS-1/4-10-I	10
	R3/8 thread	For tubing Ø 8 mm	130681	QS-3/8-8-50	50
		For tubing Ø 10 mm	130682	QS-3/8-10-50	50
		For tubing Ø 12 mm	130683	QS-3/8-12-20	20
		For tubing Ø 16 mm	164957	QS-3/8-16	1

1) Packaging unit.

## Accessories

Ordering data		Description	Part no.	Type	PU <sup>1)</sup>
Silencer					Data sheets → Internet: amte
	For M3 thread		1231120	AMTE-M-LH-M3	20
	For M5 thread		★ 1205858	AMTE-M-LH-M5	20
					Data sheets → Internet: nrh
	For M7 thread		161418	UC-M7	1
	For G1/8 thread	High flow rate	★ 2307	U-1/8	1
		Lower flow rate	161419	UC-1/8	1
	For G1/4 thread	High flow rate	★ 2316	U-1/4	1
		Lower flow rate	165004	UC-1/4	1
	For G3/8 thread	High flow rate	★ 2309	U-3/8	1
		Lower flow rate	1707427	UC-3/8	1
		Metal housing	★ 6843	U-3/8-B	1
H-rail					Data sheets → Internet: nrh
	To EN 60715, 35 x 7.5 (WxH)	2 m long	35430	NRH-35-2000	1
H-rail mounting					Data sheets → Internet: vame
	-		★ 569998	VAME-T-M4	2
Cover cap for manual override					
	Covered		540898	VMPA-HBV-B	10
	Non-detenting		540897	VMPA-HBT-B	10
	Detenting (without accessories)		8002234	VAMC-L1-CD	10
Identification holder					Data sheets → Internet: aslr
	Holder for an inscription label and cover for the retaining screw and manual override		570818	ASLR-D-L1	10
Mounting kit					Data sheets → Internet: davm
	With mounting bracket for lateral valve mounting	VUVG-L14	2568514	DAVM-MW-V1-32-V	1
		VUVG-L18	2612128	DAVM-MW-V1-50-V	1

1) Packaging unit.

## Accessories

Ordering data		Description	Part no.	Type	PU <sup>1)</sup>		
<b>Check valve</b>							
	For manifold rails VABM-L1-10...	For blocking the flow in the event of back pressure in duct 3 and 5	8047364	VABF-L1-10H-H2	10		
	For manifold rails VABM-L1-14...		8047365	VABF-L1-14H-H2	10		
<b>Flow restrictor</b>							
	For manifold rails VABM-L1-10...	For setting the flow rate during pressurisation and exhausting (for M5 threaded connection)	Nominal size: 0.5 mm	8025709	VFFG-T-M5-5	10	
			Nominal size: 0.6 mm	8025710	VFFG-T-M5-6	10	
			Nominal size: 0.7 mm	8025711	VFFG-T-M5-7	10	
			Nominal size: 0.85 mm	8025712	VFFG-T-M5-8	10	
			Nominal size: 1.05 mm	8025713	VFFG-T-M5-10	10	
			Nominal size: 1.2 mm	8025714	VFFG-T-M5-12	10	
			Nominal size: 1.55 mm	8025715	VFFG-T-M5-15	10	
		For setting the flow rate for pressurisation and exhausting (for Ø 4 mm)	Nominal size: 0.5 mm	8047346	VFFG-T-F4-5	10	
			Nominal size: 0.6 mm	8047347	VFFG-T-F4-6	10	
			Nominal size: 0.7 mm	8047348	VFFG-T-F4-7	10	
			Nominal size: 0.85 mm	8047349	VFFG-T-F4-8	10	
			Nominal size: 1.05 mm	8047350	VFFG-T-F4-10	10	
			Nominal size: 1.2 mm	8047351	VFFG-T-F4-12	10	
			Nominal size: 1.55 mm	8047352	VFFG-T-F4-15	10	
		For manifold rails VABM-L1-14...	Nominal size: 0.7 mm	8047353	VFFG-T-F6-7	10	
			Nominal size: 0.85 mm	8047354	VFFG-T-F6-8	10	
			Nominal size: 1.05 mm	8047355	VFFG-T-F6-10	10	
			Nominal size: 1.15 mm	8047356	VFFG-T-F6-11	10	
			Nominal size: 1.4 mm	8047357	VFFG-T-F6-14	10	
			Nominal size: 1.6 mm	8047358	VFFG-T-F6-16	10	
			Nominal size: 1.8 mm	8047359	VFFG-T-F6-18	10	
<b>Flow control set</b>							
	For manifold rails VABM-L1-10...	Two of each size, for M5 threaded connection		8025716	VFFG-T-M5-A-V1	14	
		Two of each size, for Ø 4 mm		8062200	VFFG-T-F4-A-V1	14	
	For manifold rails VABM-L1-14...	Two of each size, for Ø 5.8 mm		8062201	VFFG-T-F6-A-V1	14	

1) Packaging unit.

# Festo - Your Partner in Automation



## 1 Festo Inc.

5300 Explorer Drive  
Mississauga, ON L4W 5G4  
Canada

### Festo Customer Interaction Center

Tel: 1 877 463 3786  
Fax: 1 877 393 3786  
Email: [customer.service.ca@festo.com](mailto:customer.service.ca@festo.com)

## 2 Festo Pneumatic

Av. Ceylán 3,  
Col. Tequesquínáhuac  
54020 Tlalnepantla,  
Estado de México

### Multinational Contact Center

01 800 337 8669  
[ventas.mexico@festo.com](mailto:ventas.mexico@festo.com)

## 3 Festo Corporation

1377 Motor Parkway  
Suite 310  
Islandia, NY 11749

### Festo Customer Interaction Center

1 800 993 3786  
1 800 963 3786  
[customer.service.us@festo.com](mailto:customer.service.us@festo.com)

## 4 Regional Service Center

7777 Columbia Road  
Mason, OH 45040

### Connect with us



[www.festo.com/socialmedia](http://www.festo.com/socialmedia)



[www.festo.com](http://www.festo.com)