
Vacuum generators OVEL

FESTO



Key features

At a glance

Rapid reduction of the vacuum for safe placement of the workpiece by a solenoid valve to control the ejector pulse, optional


Flow control screw to adjust the ejector impulse

Electrical connection via H3 plug

Fast vacuum build-up using a solenoid valve to control the compressed air supply

Supply port, secured with wire clamp

Additional supply port for separate supply for the ejector pulse, optional, secured with wire clamp



Pressure transmitter SPTE/pressure sensor SPAE for monitoring the vacuum, optional, secured with wire clamp

Maintenance-free operation and reduced noise level by an open silencer, optional

Vacuum generator cartridge, secured with wire clamp

Vacuum port, secured with clamping clip

Housing with mounting holes

The compact vacuum generator

OVEL → page 3

- Low-cost, compact vacuum generator
- · Low weight
- Various performance levels and vacuum types
- Short switching times with integrated solenoid valves
 - Vacuum on/off
- Ejector pulse
- Simple installation with H3 plugs and push-in fittings
- Straightforward mounting with retaining screws

- Low-noise operation due to integrated silencer
- · Integrated filter
- Reduced contamination of the vacuum generator thanks to an open silencer
- Solenoid valves are switched by mechanical manual override
- Vacuum monitored by vacuum sensor
- Link up to 8 vacuum generators on a single common supply manifold.

OVTL → ovtl

The vacuum generator OVTL is a configurable module comprising vacuum generators OVEL, the common supply manifold OABM-P and connection accessories.

All products are available from the factory fully assembled.



Functional principle of OVEL

Vacuum ON/OFF

The compressed air supply is controlled by a solenoid valve. The solenoid valve can be supplied with the N/C (normally closed) switching func-

tion, i.e. the vacuum is not generated until the vacuum generator is pressurised with compressed air and the solenoid valve has been switched.

Optional ejector pulse

After the vacuum is switched off, an ejector pulse is activated and generated by a second solenoid valve to release the workpiece safely from the suction cup with connection and to quickly reduce the vacuum.

The compressed air for the ejector pulse can be supplied either via the supply port or a separate port.

Vacuum sensor, optional

The set or taught-in setpoint value for the generated vacuum is monitored by a vacuum sensor.

If the setpoint value is reached or if it is not reached due to malfunctions (e.g. leakages, dropped workpiece), the vacuum sensor emits an electrical signal.

OVEL-...-V1B/V1V/B2B/B2V:


Pressure transmitter SPTE with an analogue output (→ page 17).

Detection of analogue signals and conversion into digital signals with downstream signal converter SCDN with LCD display (→ page 22).

OVEL-...-V1PNLK/B2PNLK:

Pressure sensor SPAE with various switching outputs and LCD display, IO-Link[®] and teach-in function (→ page 19).

Peripherals overview



	ting attachments and accessories	OVELPQ	OVELP	→ Page/Internet
[1]	Vacuum generators OVEL	•	•	4
[2]	Suction gripper ESG	•	•	esg
[3]	Pressure transmitter SPTE	•	•	17
[4]	Pressure sensor SPAE	•	•	19
[5]	Plug NECU-S-M8G3/M12G3		•	22
[6]	Plug NECU-S-ECG4	•	•	22
[7]	Signal converter SCDN	•	•	22
[8]	Plug socket with cable NEBV	•	•	22
[9]	Mounting kit OABM-MK	-	•	15
[10]	Blanking plug B-M7	-	•	22
[11]	Common supply manifold OABM-P	-	•	13
[12]	Push-in fitting QS	-	•	22
[13]	Blanking plug B-1/8	-	•	22
_	Suction cup complete holder ESH	•	•	esh
-	Suction cup with connection ESS	•	•	ess
_	Vacuum filter OAFF	•	•	16

Vacuum generators OVEL

Type codes


001	Series	
OVEL	Vacuum suction nozzle, electropneumatic	
002	Vocuum generation	
	Vacuum generation	
5	Laval nozzle 0.45 mm	
7	Laval nozzle 0.7 mm	
10	Laval nozzle 0.95 mm	
003	Vacuum type	
Н	High vacuum	
L	High suction rate	
004	Size	
10	10	
15	15	
005	Supply air connection	
P	For P linking	
PQ	QS connections, metric	
006	Vacuum connection	
VM7	M7	
VQ3	Push-in connector 3 mm	
VQ4	Push-in connector 4 mm	
VQ6	Push-in connector 6 mm	
007	Exhaust connection	
RQ	QS connections, metric	
UA	Open silencer UO	
UC	Closed silencer UC	

008	Ejector pulse connection	
	Via supply air connection	
Z	Additional connection	
009	Vacuum valve	
С	Normally closed	
010	Additional function	
	Without ejector pulse	
A	Electric ejector pulse	
011	Pressure measuring range vacuum sensor	
	Without vacuum sensor	
V1	01 bar	
B2	-1 1 bar	
012	Output signal vacuum sensor	
	Without vacuum sensor	
В	1 5 V	
V	0 10 V	
PNLK	PNP or NPN or IO-Link®	
013	Electrical connection	
Н3	Connection pattern H, vertical plug	
014	Robot connection	
	None	
RA1	Universal robots	



Note

The ordering data include possible combinations.



Function

N/C, normally closed:

- With/without ejector pulse
- Push-in connectors
- Open silencer
- With/without vacuum sensor
- Prepared for common supply manifold



General technical o	lata									
Туре			OVEL-5-H	OVEL-5-L	OVEL-7-H	OVEL-7-L	OVEL-10-H/L			
Nominal width of La	ival nozzle	[mm]	0.45		0.7		0.95			
Grid dimension		[mm]	10		15		15			
Grade of filtration		[µm]	40							
Mounting position			Any							
Type of mounting			With through-hole							
			On manifold rail							
Pneumatic port 1	OVELP		Common line via mani	fold rail						
	OVELPQ-VQ	3	For tubing O.D. 3 mm	-	-		-			
	OVELPQ		For tubing O.D. 4 mm		For tubing O.D. 4 mm	For tubing O.D. 6 mm	For tubing O.D. 6 mm			
Vacuum port	OVELVQ3		For tubing O.D. 3 mm		-		-			
	OVELVQ4		For tubing O.D. 4 mm		For tubing O.D. 4 mm	-	-			
	OVELVQ6		-		_	For tubing O.D. 6 mm	For tubing O.D. 6 mm			
Pneumatic port 3	OVELUA		Silencer open							
	OVELRQ		For tubing O.D. 4 mm		For tubing O.D. 6 mm		For tubing O.D. 6 mm			
Port for ejector pulse ¹⁾	OVELZ-A		Corresponds to the sel	lected size of pneumati	c port 1					

¹⁾ If there is no ejector pulse or the ejector pulse is generated via pneumatic port 1, the additional port for the ejector pulse is sealed with a blanking plug.

Technical data – de	sign		1				
Туре		OVELUA	OVELRQ				
Design		T-shape					
Ejector	OVELH	High vacuum/standard					
characteristic	OVELL	High suction rate/standard					
Silencer design		open	_				
Integrated function		n/off valve, electric					
		Filter					
		Silencer open	-				
	OVELA	Electrical ejector pulse					
	OVELA	Flow control valve					
	OVELV1B/V1V/B2B/	Pressure transmitter					
	B2V						
	OVELV1PNLK/B2PN-	Pressure sensor					
	LK						
Valve function		Closed					
Manual override		Non-detenting					

Operating and environmental conditions					
Operating pressure	[bar]	27			
Nominal operating pressure	[MPa]	0.4			
	[bar]	4			
	[bar]	58			
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]			
Note on the operating/pilot medium		bricated operation not possible			
LABS (PWIS) conformity		VDMA24364-B1/B2-L			
Ambient temperature	[°C]	0+50			
Temperature of medium	[°C]	0 +50			
Corrosion resistance class CRC ¹⁾		2			
CE marking (see declaration of conf	formity) ²⁾	To EU EMC Directive			
Certification ²⁾		c UL us · Listed (OL)			
KC marking ³⁾		KCEMC			
Degree of protection		IP40			

¹⁾ Corrosion resistance class CRC 2 to Festo standard FN 940070

³⁾ Applies to products with vacuum sensor.

Performance data – high vacuum				
Туре		OVEL-5-H	OVEL-7-H	OVEL-10-H
Max. vacuum	[%]	89	92	92
Operating pressure for max.	[MPa]	0.42	0.45	0.38
vacuum	[bar]	4.2	4.5	3.8
	[psi]	60.9	65.25	55.1
Operating pressure for max. suction	[MPa]	0.3	0.4	0.4
rate	[bar]	3	4	4
	[psi]	43.5	58	58
Max. suction rate with respect to atmosphere	[l/min]	4	17	21
Pressurisation time at nominal operating pressure 4 bar (for 1 l volume) ¹⁾	[s]	2	1.2	1
Sound pressure level at p ₁ = 4 bar	[db(A)]	64	61	68

¹⁾ Time required to reduce the vacuum to a residual vacuum of –0.05 bar

Performance data – high suction rate										
Туре		OVEL-5-L	OVEL-7-L	OVEL-10-L						
Operating pressure for max. suction rate	[bar]	5	5	6						
Max. suction rate with respect to atmosphere	[l/min]	11	33	45						
Pressurisation time at nominal operating pressure 4 bar (for 1 l volume) ¹⁾	[s]	0.8	0.4	0.4						
Sound pressure level at p ₁ = 4 bar	[db(A)]	52	64	67						

¹⁾ Time required to reduce the vacuum to a residual vacuum of –0.05 bar

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.

Additional information: www.festo.com/catalogue/ovel → Support/Downloads.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.


Technical data – ele	ectrical connection	on								
Туре		-	OVEL without ejector pulse	OVEL with ejector pulse						
Solenoid valve										
Electrical connec-	Function		Vacuum generation	acuum generation						
tion input,			_	Ejector pulse						
	Connection typ	e	Plug	2x plugs						
	Connection tec	hnology	Plug pattern H							
	Number of pins	/wires	2							
	Plug pattern		1 3							
	Type of mounting		Snap-locking							
Operating voltage ra	ange	[V DC]	21.6 26.4							
Duty cycle		[%]	100							
Characteristic coil d	ata, 24 V DC	[W]	1.0							
Vacuum sensor										
Electrical connec-	Function		Sensor							
tion output,	Connection typ	е	Cable							
	Connection tec	hnology	Open end							
	Number of pins	/wires	3							
Cable diameter		[mm]	2.9 ±0.1							
Cable length		[m]	2.5							
Nominal conductor	cross section	[mm ²]	0.14							
Cable characteristic			Suitable for energy chains							

Technical data – vacuum sensor									
Туре		OVELV1B	OVELV1V	OVELB2B	OVELB2V	OVELV1PNLK	OVELB2PNLK		
Mechanical system									
Measurement method		Piezoresistive p	ressure sensor			Piezoresistive pressure	sensor with display		
Pressure measuring range	[MPa]	-0.1 0		-0.1 0.1		-0.1 0	-0.1 0.1		
	[bar]	-1 0		-1 1		-1 O	-1 1		
	[psi]	-14.5 0		-14.5 14.5		-14.5 0	-14.5 14.5		
Setting options		-			Teach-in				
					IO-Link®	IO-Link [®]			
					Via display and keys	Via display and keys			
Display type		-				LED display, 2-digit			
Electrical system									
Operating voltage range, sensor	[V DC]	10 30	18 30	10 30	18 30	18 30			
Switching output		-			PNP/NPN switchable				
Switching element function		-			N/C or N/O, switchable				
Switching function		_			Freely programmable				
Analogue output	[V]	1 5	0 10	1 5	0 10	_			


Materials	
Housing	Reinforced PA
Silencer	PU
Jet nozzle	Wrought aluminium alloy
Female nozzle	POM
Filter	POM
Adjusting screw	Steel
Connecting thread	POM
Screws	Steel
Cable sheath	PVC (colour: grey)
Seals	NBR
Note on materials	RoHS-compliant

Vacuum p_u as a function of operating pressure p₁

High vacuum



High suction rate




OVEL-5-H
OVEL-7-H
OVEL-10-H


OVEL-5-L
OVEL-7-L
OVEL-10-L

Evacuation time t_{evac} as a function of vacuum \textbf{p}_{u} for 1 l volume at 4 bar operating pressure

High vacuum








OVEL-5-H
OVEL-7-H
OVEL-10-H

OVEL-5-L
OVEL-7-L
OVEL-10-L

Air consumption q_n as a function of operating pressure p₁

High vacuum/high suction rate



OVEL-5
OVEL-7
OVEL-10

Download CAD data → www.festo.com


Datasheet

Dimensions

[] Without ejector pulse and vacuum sensor

[RQ] Push-in connector on pneumatic port 3

OVEL-5





[A] With ejector pulse

[UA] Open silencer on pneumatic port 3

[V1B]/[V1V]/[B2B]/[B2V]/[V1PNLK]/[B2PNLK] Vacuum sensor

OVEL-5






Туре	B1	H1	H2	Н3	H4	H5	L1	L2		L3		L4	L5	L6	L7	L8	L9
	±0.3	±0.8	±0.5	±0.5	±0.2	±0.5	±0.8	±0).8 ±2		2	±0.5	±0.5	±0.2	±0.2	±0.8	±0.8
								[RQ]	[UA]	[RQ]	[UA]						
OVEL-5										70	71					2	
OVEL-5V1B/V1V/B2B/B2V	10.3	62	9.4	13	20.4	13	42	19	20.2	81	81	27.7	9.4	13.7	15	13	59
OVEL-5V1PNLK/B2PNLK										99	99					31	
OVEL-7-H										97	114					2	
OVEL-7-HV1B/V1V/B2B/B2V	15.2	72	13.5	13	24	13.5	68.8	19	35.5	97	114	35.8	9.4	30	15	13	-
OVEL-7-HV1PNLK/B2PNLK										109	114					31	
OVEL-7-L										99	116					2	
OVEL-7-LV1B/V1V/B2B/B2V	15.2	74	13.5	13	24	13.5	68.8	19	35.5	99	116	35.8	11.4	30	15	13	_
OVEL-7-LV1PNLK/B2PNLK										111	116					31	
OVEL-10										99	116					2	
OVEL-10V1B/V1V/B2B/B2V	15.2	74	13.5	13	24	13.5	68.8	19	35.5	99	116	35.8	11.4	30	15	13	_
OVEL-10V1PNLK/B2PLNK										111	116					31	

Dimensions

Vacuum generators for UR-Plus gripper



Download CAD data → www.festo.com

Туре	B1 ±0.3	H1 ±0.8	H2 ±0.5	H3 ±0.5	H4 ±0.2	H5 ±0.5	H6 ±0.2	L1 ±0.8	L2 ±0.8	L3 ±2	L4 ±0.5	L5 ±0.5	L6 ±0.2	L7 ±0.2	L8 ±0.8	
OVEL-10VM7-UA-C-A-V1V-H3	15.2	62	13.5	13	24	13.5	25.3	68.8	35.5	116	35.8	11.4	30	15	13	1

7

D5


Dimensions


Suction gripper kit for robots

1

Ξ

2





Download CAD data → www.festo.com

- [1] Vacuum valve
- [2] Ejector valve
- [3] Suction cup with connection VAS-40-1/4-NBR
- [4] Without distance piece
- [5] With distance piece
- [6] Socket head screw M6x10
- [7] Without suction cup C and blanking plug

Туре	B1	B2	В3	D1 Ø	D2 Ø	D3 Ø	D4	D5	H1	H2	Н3	H4	H5	L1	L2	L3
OVEL-10VM7-UA-C-A-V1V-H3-RA1	24.7	47	40	84.5	50	40	G1/4	G1/8	64.5	15.8	25.1	15	11	47.2	68.2	45.5

-[3]

Ordering data – high v	acuum					
Vacuum sensor pressure measuring range	Vacuum sensor output signal	Exhaust port	Nominal width of Laval nozzle	Weight	Part no.	Туре
[bar]			[mm]	[g]		
Vacuum generators, fo	r P-links					
-1 0	PNP or NPN or IO-Link®	UC	0.45	75	8141086	OVEL-5-H-10-P-VQ4-UC-C-A-V1PNLK-H3
			0.7	92	8141087	OVEL-7-H-15-P-VQ4-UC-C-A-V1PNLK-H3
			0.95	93	8141089	OVEL-10-H-15-P-VQ6-UC-C-A-V1PNLK-H3
-	-	UC	0.45	40	8141094	OVEL-5-H-10-P-VQ4-UC-C-A-H3
			0.7	57	8141095	OVEL-7-H-15-P-VQ4-UC-C-A-H3
			0.95	58	8141097	OVEL-10-H-15-P-VQ6-UC-C-A-H3
Vacuum generators, fo	r metric QS connections					
-1 0	1 5 V	UA	0.45	71	8049046	OVEL-5-H-10-PQ-VQ4-UA-C-A-V1B-H3
			0.7	88	8049047	OVEL-7-H-15-PQ-VQ4-UA-C-A-V1B-H3
			0.95	89	8049048	OVEL-10-H-15-PQ-VQ6-UA-C-A-V1B-H3
	0 10 V	UA	0.45	71	8049049	OVEL-5-H-10-PQ-VQ4-UA-C-A-V1V-H3
			0.7	88	8049050	OVEL-7-H-15-PQ-VQ4-UA-C-A-V1V-H3
			0.95	89	8049051	OVEL-10-H-15-PQ-VQ6-UA-C-A-V1V-H3
	PNP or NPN or IO-Link®	UA	0.45	74	8049052	OVEL-5-H-10-PQ-VQ4-UA-C-A-V1PNLK-H3
		UA	0.7	91	8049053	OVEL-7-H-15-PQ-VQ4-UA-C-A-V1PNLK-H3
		UC	0.7	91	8141092	OVEL-7-H-15-PQ-VQ4-UC-C-A-V1PNLK-H3
		UA	0.95	92	8049054	OVEL-10-H-15-PQ-VQ6-UA-C-A-V1PNLK-H3
		UC	0.95	92	8141093	OVEL-10-H-15-PQ-VQ6-UC-C-A-V1PNLK-H3
-1 1	0 10 V	UA	0.45	71	8069567	OVEL-5-H-10-PQ-VQ4-UA-C-A-B2V-H3
			0.7	88	8069568	OVEL-7-H-15-PQ-VQ4-UA-C-A-B2V-H3
			0.95	88	8069569	OVEL-10-H-15-PQ-VQ6-UA-C-A-B2V-H3
	PNP or NPN or IO-Link®	UA	0.45	74	8069570	OVEL-5-H-10-PQ-VQ4-UA-C-A-B2PNLK-H3
			0.7	91	8069571	OVEL-7-H-15-PQ-VQ4-UA-C-A-B2PNLK-H3
			0.95	91	8069572	OVEL-10-H-15-PQ-VQ6-UA-C-A-B2PNLK-H3
-	_	UC	0.45	39	8141099	OVEL-5-H-10-PQ-VQ4-UC-C-A-H3
			0.7	56	8141100	OVEL-7-H-15-PQ-VQ4-UC-C-A-H3
			0.95	57	8142126	OVEL-10-H-15-PQ-VQ6-UC-C-A-H3
Vacuum generators for	UR-Plus gripper					
-1 0	0 10 V	UA	0.95	88	8129122	OVEL-10-H-15-PQ-VM7-UA-C-A-V1V-H3
Suction gripper kit for	rohots		,			
-1 0	0 10 V	UA	0.95	300	8121043	OVEL-10-H-15-PQ-VM7-UA-C-A-V1V-H3-RA1
•	- ··· ·	· .	1	1	0111019	

Vacuum generators OVEL

Ordering data – Modular product system

Ordering table				
Туре	OVEL	Conditions	Code	Enter code
Module no.	8049045			
Vacuum generator	Vacuum generator, electropneumatic		OVEL	OVEL
Nominal width of Laval nozzle [mm]	0.45		-5	
	0.7		-7	
	0.95		-10	
Ejector characteristic	High vacuum		-H	
	High suction rate		-L	
Housing size/width [mm]	10	[1]	-10	
	15	[2]	-15	
Pneumatic port 1	For pneumatic links via manifold rail		-Р	
	Push-in connectors, metric		-PQ	
Vacuum port	Push-in connector 3 mm	[3]	-VQ3	
	Push-in connector 4 mm	[4]	-VQ4	
	Push-in connector 6 mm	[5]	-VQ6	
Pneumatic port 3	Push-in connectors, metric		-RQ	
	Silencer open		-UA	
	Silencer closed	[8]	-UC	
Ejector pulse connection	Via pneumatic port 1			
	Additional port (as pneumatic port 1)		-Z	
Vacuum valve	Normally closed		-C	-C
Additional function	Without ejector pulse			
	Electrical ejector pulse	[6]	-A	
Vacuum sensor pressure measuring	Without vacuum sensor			
range	-1 0 bar		-V1	
	–1 1 bar		-B2	
Vacuum sensor output signal	Without vacuum sensor			
	1 5 V	[7]	В	
	0 10 V	[7]	٧	
	PNP or NPN or IO-Link®	[7]	PNLK	
Electrical connection	Plug pattern H, vertical plug		-H3	-H3

[1] 10 [2] 15 [3] VQ3 [4] VQ4 [5] VQ6 [6] A [7] B, V[8] UC Not with Laval nozzle nominal width 7, 10. 15 Not with Laval nozzle nominal width 5. VQ3 Only with Laval nozzle nominal width 5.

VQ4 Only with Laval nozzle nominal width 5 or Laval nozzle nominal width 7 in combination with ejector characteristic H. Only with Laval nozzle nominal width 10 or Laval nozzle nominal width 7 in combination with ejector characteristic L. Mandatory information in combination with ejector pulse port Z. Mandatory information in combination with vacuum sensor pressure measuring range B2, V1. VQ6

B, V, PNLK

Only with vacuum type H, high vacuum

Common supply manifold OABM-P

For vacuum generator OVEL-...-P

- Up to 8 vacuum generators OVEL on a common supply manifold
- Common compressed air supply via common supply manifold



On the common supply manifold vacuum generators with an additional port for the ejector pulse (OVEL-...-Z-C-A) cannot be combined with vacuum generators without an additional port (OVEL-...-C-A).



General technical data		
Pneumatic port 1		G1/8
Type of mounting		With through-hole
Min. tightening torque	[Nm]	0.3
Max. tightening torque	[Nm]	3.3


Operating and environmental conditions	
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Corrosion resistance class CRC	2 - Moderate corrosion stress

1) Corrosion resistance class CRC 2 to Festo standard FN 940070 Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.


Materials	
Sub-base	Wrought aluminium alloy
Note on materials	RoHS-compliant

Dimensions

Download CAD data → www.festo.com



Туре	B1	B2	В3	B4	D1	D2 Ø	D3 Ø	D4	H1	H2	L1	L2	L3	L4	L5	L6	T1	T2	T3
OABM-P-G3-10-2											40.5	30.5	10.5						
OABM-P-G3-10-4	30	13	23	7	G1/8	8	4.5	M7	19.5	11.5	61.5	51.5	31.5	10.5	10	5	8	4.6	6.6
OABM-P-G3-10-8											103.5	93.5	73.5						
OABM-P-G3-15-2											51.5	41.5	15.5						
OABM-P-G3-15-4	30	13	23	7	G1/8	8	4.5	M7	19.5	11.5	82.5	72.5	46.5	15.5	13	5	8	4.6	6.6
OABM-P-G3-15-8											144.5	134.5	108.5						



Download CAD data → www.festo.com

- 🖣 - Note

Combined allocation with OVEL-5 and OVEL-7/-10 is possible only with common supply manifolds OABM-...-15.

Use mounting kit OABM-MK for mounting the OVEL on the common supply manifold.

Min. tightening torque: 0.3 Nm

Max. tightening torque: 3.3 Nm

[1] Vacuum generator OVEL-5/7/10

Type		B1	B2	В3	B4	B5	В6	В7	D1	H1	H2	L1	L2	L3
OABM-P-G3-10-2	with OVEL-5											40.5	10.5	
OABM-P-G3-10-4		30	62	25	52	10	23	7	G1/8	19.5	110	61.5	31.5	10.5
OABM-P-G3-10-8												103.5	73.5	
OABM-P-G3-15-2	with OVEL-7/10											51.5	15.5	
OABM-P-G3-15-4		30	74	31	57	16	23	7	G1/8	19.5	125	82.5	46.5	15.5
OABM-P-G3-15-8												144.5	108.5	

Ordering data					
Common supply manifold	Number of device positions	CRC ¹⁾	Weight	Part no.	Туре
			[g]		
For OVEL-5	2	2	45.2	8049141	OABM-P-G3-10-2
	4	2	69.6	8049142	OABM-P-G3-10-4
	8	2	118.6	8049143	OABM-P-G3-10-8
For OVEL 5 /7 /4 O		12	50.6	00/04//	04PM P C2 45 2
For OVEL-5/7/10	2	2	59.6	8049144	OABM-P-G3-15-2
	4	2	97.1	8049145	OABM-P-G3-15-4
	8	2	172	8049146	OABM-P-G3-15-8

¹⁾ Corrosion resistance class CRC 2 to Festo standard FN 940070 Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.

Mounting kit OABM-MK

For common supply manifold OABM-P



General technical data		
Type of mounting		Via retaining clips
		Can be screwed onto manifold rail
Min. tightening torque	[Nm]	0.3
Max. tightening torque	[Nm]	3.3

Operating and environmental conditions	erating and environmental conditions								
LABS (PWIS) conformity	VDMA24364-B1/B2-L								
Corrosion resistance class CRC ¹⁾	2 - Moderate corrosion stress								

¹⁾ Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.

Materials	
Hollow bolt	Wrought aluminium alloy
Seals	NBR
Note on materials	RoHS-compliant

Ordering data							
	Weight	Part no.	Туре				
	[g]						
For common supply manifold OABM-P	7	8065850	OABM-MK-G3				

Vacuum filter OAFF



General technical data		
Type of mounting		Push-on
		Snap-in
Grade of filtration	[µm]	40
Ejector pulse suitability	[bar]	≤7

Operating and environmental co	onditions	
Operating pressure	[kPa]	-95 0
	[bar]	-0.95 0
	[psi]	-13.775 0
Operating medium		Atmospheric air based on ISO 8573-1:2010 [7:-:-]
LABS (PWIS) conformity		VDMA24364-B1/B2-L
Ejector pulse suitability	[MPa]	0.7
	[bar]	7
	[psi]	101.5

Materials		
Туре	OAFF-G3-5	OAFF-G3-7
Housing	POM	
Filter	Fabric, PA	
Seals	-	NBR
Note on materials	RoHS-compliant	


Ordering data					
	Weight	Part no.	Туре	PU ¹⁾	
	[g]				
For vacuum generator OVEL-5	1	8068944	OAFF-G3-5	10	
For vacuum generator OVEL-7/10	1.5	8068945	OAFF-G3-7	10	

¹⁾ Packaging unit

Pressure transmitter SPTE

(Order code in modular product system: OVEL-...-V1B/V1V/B2B/B2V, OVTL-...-V)

- Pressure measuring ranges
 -1 ... 0 bar or -1 ... 1 bar
- Analogue outputs 1 ... 5 V or 0 ... 10 V



Detection of analogue signals and conversion into digital signals with downstream signal converter SCDN with LCD display (→ page 22).



General technical data		
Certification	RCM	
	c UL us - Recognized (OL)	
CE marking (see declaration of conformity) ¹⁾	To EU EMC Directive	
Note on materials	RoHS-compliant	

1) For information about the area of use, see the EC declaration of conformity at: www.festo.com/sp → Certificates.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Input signal/measuring element			
Туре		SPTE-V1R	SPTE-B2R
Measured variable		Relative pressure	
Measurement method		Piezoresistive pressure sensor	
Pressure measuring range start	[bar]	0	-1
value			
Pressure measuring range end	[bar]	-1	1
value			
Max. overload pressure	[bar]	5	5
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]	
Note on the operating/pilot medium	1	Lubricated operation possible	
Temperature of medium	[°C]	050	
Ambient temperature	[°C]	0 50	

Output, general		
Accuracy ±FS ¹⁾	[%]	3 (at room temperature of approx. 23°C)
		4 (in ambient temperature range 0 50°C)
Repetition accuracy ±FS ¹⁾	[%]	0.3
Temperature coefficient ±FS/K ¹⁾	[%]	0.05

1) % FS = % of the measuring range (full scale)

Analogue output			
Туре		SPTEV-2.5K	SPTEB-2.5K
Analogue output	[V]	010	15
Rise time	[ms]	1	
Min. load resistance of voltage	[kΩ]	15	
output			

Output, additional data					
Short circuit current rating		For all electrical connections			
Electronics					
Type		SPTEV-2.5K	SPTEB-2.5K		
Operating voltage range DC	[V]	18 30	10 30		
Reverse polarity protection		For all electrical connections			
Electromechanics Electrical connection		Cable, 3-core, open end			
Electrical connection Cable length	[]	Cable, 3-core, open end 2.5			
Cable length	[m]	2.3			
Mechanical systems					
Type of mounting		Pin-type connection			
Mounting position		Any			
Pneumatic port		Cartridge 10 mm			
Product weight	[g]	35			
Information on materials: Housi	ng	Reinforced PA			


Immission/Emission

 Degree of protection
 IP40

 Corrosion resistance class CRC¹)
 2

¹⁾ Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.




Ordering data							
Pneumatic port	Electrical connection	Pressure measuring range	Analogue output		Order code in the modular product system		Туре
		[bar]	[V]	OVEL	OVTL		
Cartridge 10 mm	Cable, 3-core, open	-1 0	0 10	V1V	V	8025974	SPTE-V1R-PC10-V-2.5K
	end		1 5	V1B	-	8025975	SPTE-V1R-PC10-B-2.5K
		-1 1	0 10	B2V	-	8025976	SPTE-B2R-PC10-V-2.5K

Pressure sensor SPAE

(Order code in the modular product system: OVEL-...-V1PNLK/B2PNLK, OVTL-...-PNLK)

- Pressure measuring ranges
 - $-1 \dots 0$ bar or $-1 \dots 1$ bar
- Switching output PNP/NPN, switchable
- IO-Link®
- LCD display
- Teach function





General technical data		
Certification	RCM	
	c UL us - Recognized (OL)	
CE marking (see declaration of conformity) ¹⁾	To EU EMC Directive	
Note on materials	RoHS-compliant	

1) For information about the area of use, see the EC declaration of conformity at: www.festo.com/sp → Certificates.

If the devices are subject to usage restrictions in residential, commercial or light-industrial environments, further measures for the reduction of the emitted interference may be necessary.

Input signal/measuring element	input signal/measuring element					
Туре		SPAE-V1R	SPAE-B2R			
Measured variable		Relative pressure				
Measurement method		Piezoresistive pressure sensor				
Pressure measuring range start	[bar]	0	-1			
value						
Pressure measuring range end	[bar]	-1	1			
value						
Max. overload pressure	[bar]	5	5			
Operating medium		Compressed air to ISO 8573-1:2010 [7:4:4]				
Note on the operating/pilot medium		Lubricated operation possible				
Temperature of medium	[°C]	O 50				
Ambient temperature	[°C]	0 50				

Signal processing	
Resolution ADC	10 bits

Output, general				
Accuracy ±FS ¹⁾	[%]	1.5 (at room temperature of approx. 23°C)		
	2.5 (in ambient temperature range 0 50°C)			
Repetition accuracy ±FS ¹⁾	[%]	0.3		
Temperature coefficient ±FS/K ¹⁾	[%]	0.05		

1) % FS = % of the measuring range (full scale)


Switching output		
Switching output		PNP/NPN switchable
Switching function		Freely programmable
Switching element function		N/C or N/O, switchable
Max. output current	[mA]	100

Measured value display	
Display range start value [% FS]	0
Display range end value [% FS]	99
Output, additional data	
Short circuit current rating	For all electrical connections
Communication interface	
Protocol	IO-Link®
IO-Link®, protocol version	Device V 1.1
IO-Link [®] , profile	Smart sensor profile
IO-Link [®] , function classes	Binary data channel (BDC)
	Diagnostics
	Identification
	Process data variable (PDV)
	Teach channel
IO-Link [®] , communication mode	COM2 (38.4 kBd)
IO-Link®, SIO mode support	Yes
IO-Link®, port class	A
IO-Link®, process data width OUT	0 bytes
IO-Link®, process data width IN	2 bytes
IO-Link®, process data contents IN	2 bit BDC (pressure monitoring)
	14 bit PDV (pressure measured value)
IO-Link®, minimum cycle time [ms]	3
IO-Link®, data memory required	0.5 KB
Electronics	
Operating voltage range DC [V]	18 30
Reverse polarity protection	For all electrical connections
Electromechanics	
Electrical connection	Cable, 3-core, open end
Cable length [m]	2.5
-	
Mechanical systems	
Type of mounting	Pin-type connection
Mounting position	Any
Pneumatic port	Cartridge 10 mm
Product weight [g]	40
Information on materials: Housing	Reinforced PA
Display/operation	
Display type	LED display, 2-digit
Displayable units	% FS
Switching status indication	Yellow LED
Setting options	Via display and keys, teach-in, IO-Link®
Threshold value setting range [%]	198
Protection against tampering	PIN code

Immission/Emission	
Degree of protection	IP40
Corrosion resistance class CRC ¹⁾	2

¹⁾ Corrosion resistance class CRC 2 to Festo standard FN 940070

Moderate corrosion stress. Indoor applications in which condensation can occur. External visible parts with primarily decorative surface requirements that are in direct contact with a normal industrial environment.



Ordering data						
Pneumatic port	Electrical connection	Pressure measuring range	Order code in the modular product system		ar product system Part no. Type	
		[bar]	OVEL	OVTL		
Cartridge 10 mm	Cable, 3-core, open	-1 0	V1PNLK	PNLK	8025978	SPAE-V1R-PC10-PNLK-2.5K
	end	-1 1	B2PNLK	_	8025979	SPAE-B2R-PC10-PNLK-2.5K

dering data –	Electrical connection			Part no.	Datasheets → I	
					Туре	
	Plug M8x1, 3-pin, straight,	nsulation displacement connector		562024	NECU-S-M8G3-HX	
	Plug M12x1, A-coded, 3-pin	, straight, insulation displacement co	nnector	562027	NECU-S-M12G3-HX	
lering data –	Plug NECU-S-ECG4		·	- :	Datasheets → I	nternet: ne
• •	Electrical connection			Part no.	Туре	
	Plug, square design, 4-pin,	straight, insulation displacement conr	nector	570922	NECU-S-ECG4-HX-Q3	
		:	:			
ering data –	Signal converter SCDN				Datasheets →	Internet: s
	Measured variable			Part no.	Туре	
<u>~</u>	Voltage			8035555	SCDN-2V-EC4-PNLK-L1	
	Voltage			8035555		
aring data				8035555	SCDN-2V-EC4-PNLK-L1	ntornot, n
ering data –	Plug socket with cable NEBV Electrical connection		Cable length [m]	8035555		nternet: n
ering data –	Plug socket with cable NEBV Electrical connection 2-pin socket	Flying leads	Cable length [m]		SCDN-2V-EC4-PNLK-L1 Datasheets → I	nternet: n
ering data –	Plug socket with cable NEBV Electrical connection	Flying leads Open end	0.5	Part no.	Datasheets → I	nternet: n
ering data –	Plug socket with cable NEBV Electrical connection 2-pin socket		0.5 1 2.5	Part no. 566654 566655 566656	Datasheets → I Type NEBV-H1G2-KN-0.5-N-LE2 NEBV-H1G2-KN-1-N-LE2 NEBV-H1G2-KN-2.5-N-LE2	nternet: n
ering data –	Plug socket with cable NEBV Electrical connection 2-pin socket Plug pattern H	Open end	0.5 1 2.5 5	Part no. 566654 566655 566656 566657	Datasheets → I Type NEBV-H1G2-KN-0.5-N-LE2 NEBV-H1G2-KN-1-N-LE2 NEBV-H1G2-KN-2.5-N-LE2 NEBV-H1G2-KN-3-N-LE2	nternet: n
ering data –	Plug socket with cable NEBV Electrical connection 2-pin socket Plug pattern H 2-pin socket	Open end Cable	0.5 1 2.5 5 0.5	Part no. 566654 566655 566656 566657 566658	Datasheets → I Type NEBV-H1G2-KN-0.5-N-LE2 NEBV-H1G2-KN-1-N-LE2 NEBV-H1G2-KN-2.5-N-LE2 NEBV-H1G2-KN-5-N-LE2 NEBV-H1G2-KN-5-N-LE2	nternet: n
ering data –	Plug socket with cable NEBV Electrical connection 2-pin socket Plug pattern H	Open end	0.5 1 2.5 5 0.5	Part no. 566654 566655 566656 566657 566658 566659	Datasheets → I Type NEBV-H1G2-KN-0.5-N-LE2 NEBV-H1G2-KN-1-N-LE2 NEBV-H1G2-KN-2.5-N-LE2 NEBV-H1G2-KN-5-N-LE2 NEBV-H1G2-P-0.5-N-LE2 NEBV-H1G2-P-0.5-N-LE2	nternet: n
ering data –	Plug socket with cable NEBV Electrical connection 2-pin socket Plug pattern H 2-pin socket	Open end Cable	0.5 1 2.5 5 0.5 1 2.5	Part no. 566654 566655 566656 566657 566658 566659	Datasheets → I Type NEBV-H1G2-KN-0.5-N-LE2 NEBV-H1G2-KN-1-N-LE2 NEBV-H1G2-KN-2.5-N-LE2 NEBV-H1G2-KN-5-N-LE2 NEBV-H1G2-P-0.5-N-LE2 NEBV-H1G2-P-1-N-LE2 NEBV-H1G2-P-1-N-LE2	nternet: n
ering data –	Plug socket with cable NEBV Electrical connection 2-pin socket Plug pattern H 2-pin socket	Open end Cable	0.5 1 2.5 5 0.5	Part no. 566654 566655 566656 566657 566658 566659	Datasheets → I Type NEBV-H1G2-KN-0.5-N-LE2 NEBV-H1G2-KN-1-N-LE2 NEBV-H1G2-KN-2.5-N-LE2 NEBV-H1G2-KN-5-N-LE2 NEBV-H1G2-P-0.5-N-LE2 NEBV-H1G2-P-0.5-N-LE2	internet: n
	Plug socket with cable NEBV Electrical connection 2-pin socket Plug pattern H 2-pin socket Plug pattern H	Open end Cable	0.5 1 2.5 5 0.5 1 2.5	Part no. 566654 566655 566656 566657 566658 566659	Datasheets → I Type NEBV-H1G2-KN-0.5-N-LE2 NEBV-H1G2-KN-1-N-LE2 NEBV-H1G2-KN-2.5-N-LE2 NEBV-H1G2-KN-5-N-LE2 NEBV-H1G2-P-0.5-N-LE2 NEBV-H1G2-P-1-N-LE2 NEBV-H1G2-P-1-N-LE2	nternet: n
	Plug socket with cable NEBV Electrical connection 2-pin socket Plug pattern H 2-pin socket	Open end Cable	0.5 1 2.5 5 0.5 1 2.5	Part no. 566654 566655 566656 566657 566658 566659	Datasheets → I Type NEBV-H1G2-KN-0.5-N-LE2 NEBV-H1G2-KN-1-N-LE2 NEBV-H1G2-KN-2.5-N-LE2 NEBV-H1G2-KN-5-N-LE2 NEBV-H1G2-P-0.5-N-LE2 NEBV-H1G2-P-1-N-LE2 NEBV-H1G2-P-1-N-LE2	nternet: n
	Plug socket with cable NEBV Electrical connection 2-pin socket Plug pattern H 2-pin socket Plug pattern H Blanking plug B	Open end Cable	0.5 1 2.5 5 0.5 1 2.5	Part no. 566654 566655 566656 566657 566658 566659 566660 566661	Datasheets → I Type NEBV-H1G2-KN-0.5-N-LE2 NEBV-H1G2-KN-1-N-LE2 NEBV-H1G2-KN-5-N-LE2 NEBV-H1G2-F0.5-N-LE2 NEBV-H1G2-P-0.5-N-LE2 NEBV-H1G2-P-1-N-LE2 NEBV-H1G2-P-1-N-LE2 NEBV-H1G2-P-1-N-LE2	

¹⁾ Packaging unit.

Ordering data – Push-in fitting QS							
	Pneumatic port			Туре	PU ¹⁾		
	G1/8	Tubing O.D. 8 mm	186098	QS-G1/8-8	10		
	G1/8	Tubing O.D. 8 mm	186109	QS-G1/8-8-I	10		

¹⁾ Packaging unit.